



Representative

**Catalog Number:** 3118  
**Product ID:** 7TAA106030R0003  
**UPC Number:** 78621003118  
**EAN Number:** 05414363140818  
**Status:** Active

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 1-1/4 Inch, Knockout Size 1-1/4 Inch, Cable Range 1.562 to 1.750 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

- The tough lining of insulation and the Tite-Bite principles make these connectors a must when conductors are subject to conditions of vibration or strain.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Unique Saddle Design Firmly Secures Cable In Place, Provides Holding Power In Excess of Listing Agency Requirements and Assures High Quality Bonding
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018, CSA 2884
Size	1-1/4 Inch
Connection	Straight
Conductor Range	1.562 to 1.750 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Total length	34.13mm

#### Packaging

Inner Quantity	5
Inner Dimensions (inches)	4x4.5x6
Outer Quantity	10
Outer Dimensions (inches)	8.9x5.4x7
Weight Uom	53.5 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)