LG Neon®r

LG365Q1C-V5

365W

LG Neon R is LG's highest efficiency module in the market and provides world-class performance. The unique, back-contact cell structure eliminates electrodes on the front which maximizes the collection of light and improves overall reliability. LG Neon R features an enhanced warranty, improved aesthetics on residential roof-tops, and the highest performance and durability under real-world conditions.







60

Features



Aesthetic Roof

LG NeON[®] R has been designed with aesthetics in mind: the lack of any electrodes on the front creates an improved, modern aesthetic.



Extended Product Warranty

LG has extended the product warranty of the NeON® R to 25 years, which is top level in the industry.



Better Performance on a Sunny Day

LG NeON[®] R now performs better on sunny days, thanks to its improved temperature coefficient.



More generation per square meter

The LG NeON[®] R has been designed to significantly enhance its output, making it efficient even in limited space.

About LG Electronics

LG Electronics is a global leader in electronic products in the clean energy markets by offering solar PV panels and energy storage systems. The company first embarked on a solar energy source research program in 1985, supported by LG Group's vast experience in the semi-conductor, LCD, chemistry and materials industries. In 2010, LG Solar successfully released its first MonoX® series to the market, which is now available in 32 countries. The NeON® (previous MonoX® NeON), NeON®2, NeON®2 BiFacial won the "Intersolar AWARD" in 2013, 2015 and 2016, which demonstrates LG's leadership and innovation in the solar industry.



LG NeON®R

LG365Q1C-V5

General Data

Cell Properties (Material/Type)	Monocrystalline / N-type		
Cell Maker	LG		
Cell Configuration	60 Cells (6 x 10)		
Module Dimensions (L x W x H)	1,700mm x 1,016mm x 40mm		
Weight	17.5 kg		
Glass (Thickness / Material)	2.8mm / Tempered Glass with AR Coating		
Backsheet (Color)	White		
Frame (Material)	Anodized Aluminium		
Junction Box (Protection Degree)	IP68 with 3 Bypass Diodes		
Cables (Length)	1,000mm x 2EA		
Connector (Type / Maker)	MC 4 / MC		

Certifications and Warranty

IEC 61215-1/-1-1/2:2016, IEC 61730-1/2:2016,		
UL 1703		
ISO 9001, ISO 14001, ISO 50001		
OHSAS 18001		
IEC 61701:2012 Severity 6		
IEC 62716:2013		
Type 1		
Class C (UL 790)		
25 Years		
Linear Warranty*		

* 1) 1st year: 98%, 2) After 1st year: 0.3% annual degradation, 3) 25 years: 90.8%

Temperature Characteristics


NMOT*	[°C]	44 ± 3
Pmax	[%/°C]	-0.30
Voc	[%/°C]	-0.24
lsc	[%/°C]	0.037

* NMOT (Nominal Module Operating Temperature): Irradiance 800 W/m2, Ambient temperature 20 °C, Wind speed 1 m/s, Spectrum AM 1.5

Electrical Properties (NMOT)

Model		LG365Q1C-V5
Maximum Power (Pmax)	[W]	275
MPP Voltage (Vmpp)	[V]	36.6
MPP Current (Impp)	[A]	7.51
Open Circuit Voltage (Voc)	[V]	40.2
Short Circuit Current (Isc)	[A]	8.70

I-V Curves



Life's Good

LG Electronics Inc. Solar Business Division 2000 Millbrook Drive Lincolnshire, IL 60069 www.lg-solar.com

Electrical Properties (STC*)

Model		LG365Q1C-V5	
Maximum Power (Pmax)	[W]	365	
MPP Voltage (Vmpp)	[V]	36.7	
MPP Current (Impp)	[A]	9.95	
Open Circuit Voltage (Voc,±5%)	[V]	42.8	
Short Circuit Current (Isc, ± 5%)	[A]	10.80	
Module Efficiency	[%]	21.1	
Power Tolerance	[%]	0~+3	

* STC (Standard Test Condition): Irradiance 1000 W/m², Cell temperature 25 °C, AM 1.5

Operating Conditions


Operating Temperature	[°C]	-40 ~+90		
Maximum System Voltage	[V]	1,000		
Maximum Series Fuse Rating	[A]	20		
Mechanical Test Load (Front)	[Pa/psf]	5,400 / 113		
Mechanical Test Load (Rear)	[Pa/psf]	4,000 / 83.5		
* Tast Load - Design v Safaty Easter (1 E)				

* Test Load = Design x Safety Factor (1.5)

Packaging Configuration

Number of Modules per Pallet	[EA]	25		
Number of Modules per 40ft HQ Container	[EA]	650		
Packaging Box Dimensions (L x W x H)	[mm]	1,750 x 1,120 x 1,221		
Packaging Box Gross Weight	[kg]	473		

Dimensions (mm / inch)



Product specifications are subject to change without notice. LG365Q1C-V5_US_Ver01.pdf



© 2019 LG Electronics. All rights reserved.

