


LG NeON[®] 2 Black


LG320N1K-V5



60

320W

The LG NeON[®] 2 is LG's best selling solar module, and is one of the most powerful and versatile modules on the market today. Featuring LG's Cello Technology, the LG NeON[®] 2 increases power output. New updates include an extended performance warranty from 86% to 90.08% to give customers higher performance and reliability.



Features



Enhanced Performance Warranty

LG NeON[®] 2 Black has an enhanced performance warranty. After 25 years, LG NeON[®] 2 Black is guaranteed at least 90.08% of initial performance.



Enhanced Product Warranty

LG has extended the warranty of the NeON[®] 2 Black to 25 years including labor, which is top level in the industry.



Better Performance on a Sunny Day

LG NeON[®] 2 Black now performs better on sunny days, thanks to its improved temperature coefficient.



Roof Aesthetics

LG NeON[®] 2 Black has been designed with aesthetics in mind using thinner wires that appear all black at a distance. LG NeON[®] 2 Black can increase the value of a property with its modern design.

When you go solar, ask for the brand you can trust: LG Solar

About LG Electronics

LG Electronics is a global leader in electronic products in the clean energy markets by offering solar PV panels and energy storage systems. The company first embarked on a solar energy source research program in 1985, supported by LG Group's vast experience in the semi-conductor, LCD, chemistry and materials industries. In 2010, LG Solar successfully released its first MonoX[®] series to the market, which is now available in 32 countries. The NeON[®] (previous MonoX[®] NeON), NeON[®]2, NeON[®]2 BiFacial won the "Intersolar AWARD" in 2013, 2015 and 2016, which demonstrates LG's leadership and innovation in the solar industry.

LG Solar

LG320N1K-V5

General Data

Cell Properties (Material/Type)	Monocrystalline/N-type
Cell Maker	LG
Cell Configuration	60 Cells (6 x 10)
Number of Busbars	12EA
Module Dimensions (L x W x H)	1,686mm x 1,016mm x 40 mm
Weight	17.1 kg
Glass (Material)	Tempered Glass with AR Coating
Backsheet (Color)	Black
Frame (Material)	Anodized Aluminium
Junction Box (Protection Degree)	IP 68 with 3 Bypass Diodes
Cables (Length)	1,000mm x 2EA
Connector (Type/Maker)	MC 4/MC

Certifications and Warranty

Certifications	IEC 61215-1/-1-1/2:2016, IEC 61730-1/2:2016, UL 1703 ISO 9001, ISO 14001, ISO 50001 OHSAS 18001
Salt Mist Corrosion Test	IEC 62701:2012 Severity 6
Ammonia Corrosion Test	IEC 62716:2013
Module Fire Performance	Type 2 (UL 1703)
Fire Rating	Class C (UL 790, ULC/ORD C 1703)
Solar Module Product Warranty	25 Years
Solar Module Output Warranty	Linear Warranty*

Improved: 1st Year 98%, from 2-24th year: 0.33%/year down, after 25th year: 90.08%

Temperature Characteristics


NMOT*	[°C]	42 ± 3
Pmax	[%/°C]	-0.36
Voc	[%/°C]	-0.27
Isc	[%/°C]	0.03

* NMOT (Nominal Module Operating Temperature): Irradiance 800 W/m², Ambient temperature 20 °C, Wind speed 1 m/s, Spectrum AM 1.5

Electrical Properties (NMOT)

Model	LG320N1K-V5	
Maximum Power (Pmax)	[W]	239
MPP Voltage (Vmpp)	[V]	31.2
MPP Current (Impp)	[A]	7.67
Open Circuit Voltage (Voc)	[V]	38.3
Short Circuit Current (Isc)	[A]	8.19

I-V Curves



Electrical Properties (STC*)

Model	LG320N1K-V5	
Maximum Power (Pmax)	[W]	320
MPP Voltage (Vmpp)	[V]	33.3
MPP Current (Impp)	[A]	9.62
Open Circuit Voltage (Voc ± 5%)	[V]	40.8
Short Circuit Current (Isc ± 5%)	[A]	10.19
Module Efficiency	[%]	18.7
Power Tolerance	[%]	0 ~ +3

* STC (Standard Test Condition): Irradiance 1000 W/m², cell temperature 25 °C, AM 1.5

Operating Conditions

Operating Temperature	[°C]	-40 ~ +90
Maximum System Voltage	[V]	1,000(UL), 1000(IEC)
Maximum Series Fuse Rating	[A]	20
Mechanical Test Load (Front)	[Pa/psf]	5,400/113
Mechanical Test Load (Rear)	[Pa/psf]	4,000/84

* Test Load = Design load x Safety Factor (1.5)

Packaging Configuration

Number of Modules per Pallet	[EA]	25
Number of Modules per 40ft HQ Container	[EA]	650
Packaging Box Dimensions (L x W x H)	[mm]	1,750 x 1,120 x 1,221
Packaging Box Gross Weight	[kg]	464

Dimensions (mm/inch)

