



Representative Image

Catalog No. TF225R

Description: ENCLOSURE NEMA 3R 225A

UPC No 783164007381

Home > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: For 250 amp rating, copper cable must be used.

Enclosure includes removable closing cap.

ACCESSORIES:

Neutral Kit(non-GF applications):TNIA225
Raintight Hubs: TC150, TC200, TC250, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	F225, SF250
Amperage	250 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5498SH2
GSA Compliance	No

Dimensions

Height	30.8 in
Depth	6.2 in
Width	10.0 in
Weight	23.7 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 3R enclosure, 225 amp max. Product Number TF225R. 1 page outline drawing in .pdf format.	139C5498-SH2	Drawings-Outline and Dimensional

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.