

## PSH-1280FR 12 Volt 8.5 AH

Rechargeable Sealed Lead Acid Battery  
HIGH-RATE SERIES




We've Got The Power.™






### Terminals: (mm)

- F2 - Quick disconnect tabs, 0.250" x 0.032" - Mate with AMP. INC FASTON "250" series



### Physical Dimensions: in (mm)



L: 5.95 (151) W: 2.56 (65) H: 3.72 (94.5) HT: 3.90 (99)

Tolerances are +/- 0.04 in. (+/- 1mm) and +/- 0.08 in. (+/- 2mm) for height dimensions. All data subject to change without notice.

### Features

- Absorbent Glass Mat (AGM) technology for superior performance
- Designed specifically for high-rate discharge (UPS) applications
- 36 Watts/cell for 15 min. of constant power
- Rugged plastic case and cover, flame retardant to UL94 V-0
- Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified
- U.L. recognized under file number MH 20845

### Performance Specifications

**Nominal Voltage** ..... 12 volts (6 cells)

#### Nominal Capacity

20-hr.	(400mA to 10.50 volts)	8.50 AH
10-hr.	(810mA to 10.50 volts)	8.10 AH
5-hr.	(1.5A to 10.20 volts)	7.50 AH
1-hr.	(5.27A to 9.00 volts)	5.27 AH
15-min.	(17.5A to 9.00 volts)	4.38 AH

**Approximate Weight** ..... 5.75 lbs. (2.61 kg)

**Energy Density (20-hr. rate)** ..... 1.81 W-h/in<sup>3</sup> (110.63 W-h/l)

**Specific Energy (20-hr. rate)** ..... 17.00 W-h/lb (37.48 W-h/kg)

**Internal Resistance (approx.)** ..... 15 milliohms

**Max Discharge Current (7 Min.)** ..... 25.5 amperes

**Max Short-Duration Discharge Current (10 Sec.)** .... 85.0 amperes

#### Shelf Life (% of nominal capacity at 68°F (20°C))

1 Month	97%
3 Months	91%
6 Months	83%

#### Operating Temperature Range

Charge ..... -4°F (-20°C) to 122°F (50°C)

Discharge ..... -40°F (-40°C) to 140°F (60°C)


**Case** ..... ABS Plastic (UL94 V-0 flame retardant)

**Power-Sonic Chargers**.....PSC-12800A, 12800A-C


### Constant Power Discharge Ratings

MODEL	FINAL VOLTAGE	WATTS PER CELL @ 25° C						
		5 MIN	10 MIN	15 MIN	20 MIN	30 MIN	45 MIN	60 MIN
PSH-1280FR	1.75	65	43	35	24	17.5	14.8	12.8
	1.70	66	44	36	24.3	18.7	15	12.9
	1.67	67	45	37	24.7	19.5	15.5	13

### Discharge Time vs. Discharge Current



### Discharge Characteristics



### Charging

Cycle Applications: Limit initial current to 2.55A. Charge until battery voltage (under charge) reaches 14.4 to 14.7 volts at 68°F (20°C). Hold at 14.4 to 14.7 volts until current drops to under 85mA. Battery is fully charged under these conditions, and charger should be disconnected or switched to "float" voltage.


"Float" or "Stand-By" Service: Hold battery across constant voltage source of 13.5 to 13.8 volts continuously. When held at this voltage, the battery will seek its own current level and maintain itself in a fully charged condition.

Note: Due to the self-discharge characteristics of this type of battery, it is imperative that they be charged within 6 months of storage, otherwise permanent loss of capacity might occur as a result of sulfation.

### Chargers

Power-Sonic offers a wide range of chargers suitable for batteries up to 100AH. Please refer to the Charger Selection Guide in our specification sheets for "C-Series Switch Mode Chargers" and "Transformer Type A and F Series". Please contact our Technical department for advice if you have difficulty in locating suitable models.

### Shelf Life & Storage



### Further Information

Please refer to our website [www.power-sonic.com](http://www.power-sonic.com) for a complete range of useful downloads, such as product catalogs, material safety data sheets (MSDS), ISO certification, etc..

### Contact Information

DOMESTIC SALES  
Tel: +1-619-661-2020  
Fax: +1-619-661-3650  
[national-sales@power-sonic.com](mailto:national-sales@power-sonic.com)

CUSTOMER SERVICE  
Tel: +1-619-661-2030  
Fax: +1-619-661-3648  
[customer-service@power-sonic.com](mailto:customer-service@power-sonic.com)

TECHNICAL SUPPORT  
Tel: +1-619-661-2020  
Fax: +1-619-661-3648  
[support@power-sonic.com](mailto:support@power-sonic.com)

INTERNATIONAL SALES  
Tel: +1-650-364-5001  
Fax: +1-650-366-3662  
[international-sales@power-sonic.com](mailto:international-sales@power-sonic.com)