

Project:

Type:

Prepared By:

Date:



UPC: 19813749846



Features and Benefits

SMALL REFLECTOR REPLACEMENT - Replaces conventional small-reflector lamps

ENERGY SAVINGS - Save up to 85% on energy

25,000-HOUR LIFESPAN - Long-life product

DAMP RATED - Suitable for damp locations

DIMMABLE - Compatible with most common dimmer models

80 CRI - Ideal for general lighting applications

Technical Specifications

Product Type	Small-Reflector
Bulb Shape	PAR16
Wattage	6.5W
Wattage Equivalency	50W Halogen
Typical Lumen Output	500
Efficacy	77 lm/W
Color Temperature	3000K Warm White
CRI	80
Base Type	E26
L70 Lifespan	25,000 hours
Operating Temperature	-20°C - 45°C
Dimmable	Yes, down to 20%
Beam Angle	40°
Warranty	4-Year, No-Compromise Warranty
For Use in Emergency Fixtures	No
For Use Outdoors in Open Fixtures	No


Electrical Characteristics

Input Voltage	120V
Power Factor	0.7
Flicker	<30%

Listings

UL Listed	Yes
ENERGY STAR V2.0	This product is ENERGY STAR® Version 2.0 Certified
Energy Star ID	2331239
CEC Status	Not lawful for sale in California

Light Distribution



Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	12	8.6	6.5	3.7
PALLET	4608	42.9	39	48.1

Dimension

