



Representative Image

### Catalog No. GPS2BHAR

Description: MMS HIGH BK 24 - 32 AMPS

UPC No 453891501253

Home > Starters > IEC > Manual Motor Starter - SURION

- MANUAL MOTOR STARTER T+M PROT. GPS2 24-32A HIGH BREAKING  
- Pack-1

#### Descriptors

Category	Manual Motor Starter - SURION
GO Schedule	CC

#### Specifications

Rated Current	32.0 A
Capacity	GPS2BH - High breaking capacity
Instantaneous short-circuit release (A)	416
Rated power 3 phase motors at 220/230Vac Pn (hp)	10
Rated power 3 phase motors at 400Vac Pn (hp)	10
Rated power 3 phase motors at 440Vac Pn (hp)	20
Rated power 3 phase motors at 500/525Vac Pn (hp)	25
Rated power 3 phase motors at 660/690Vac Pn (hp)	22 hp
Rated service short-circuit breaking cap 220/230V Ics kA	65
Rated service short-circuit breaking cap 400V Ics kA	50
Rated service short-circuit breaking cap 440V Ics kA	10
Rated service short-circuit breaking cap 500/525V Ics kA	9
Rated service short-circuit breaking cap 600V Ics kA	4
Rated service short-circuit breaking cap 690V Ics kA	4
Rated ultimate short-circuit breaking cap 220/230V Icu kA	100
Rated ultimate short-circuit breaking cap 400V Icu kA	25
Rated ultimate short-circuit breaking cap 440V Icu kA	25
Rated ultimate short-circuit breaking cap 500/525V Icu kA	10
Rated ultimate short-circuit breaking cap 600V Icu kA	5
Rated ultimate short-circuit breaking cap 690V Icu kA	5
Series	Surion - GPS2B - Thermal and magnetic protection (Ie max 63A)
Thermal current setting range (A)	24 - 32 A
Trip class IEC 60947-4-1	Class 10
Single Phase Horsepower @ 115V	2
Single Phase Horsepower @ 230V	5
FLA Adjustment Range	24 - 32 A
Max. Fuse Size (A)	125
Max Circuit Breaker Size (A)	125
Max. Fuse or Circuit Breaker Size - Group Installation (A)	1500
Rated Breaking Capacity @ 277Y/480V - Combination Starter (kA)	50

## Specifications

Minimum Contactor Size	CL04
GSA Compliance	No

## Dimensions

Weight	1.8 lb
Width	55.0 mm

## Publications

Title	Publication No.	Publication Type
<a href="#">IECMMS GPS2BH 55mm Rotary</a>		
GEP1260-06-002IECMMS GPS2BH 55mm Rotary	GEP1260-06-002	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.