

Project:

Type:

Prepared By:

Date:



UPC: 19813750453



Features and Benefits

REFLECTOR REPLACEMENT - Replacement for incandescent and halogen BR reflector lamps

ENERGY SAVINGS - Save up to 85% on energy

25,000-HOUR LIFESPAN - Long-life product

DAMP RATED - Suitable for damp locations

ENCLOSED FIXTURE RATED - May be used in both enclosed and open fixtures

DIMMABLE - Compatible with most common dimmer models

SHATTERPROOF - Plastic lamps for rugged applications

110° + BEAM ANGLE - Wide beam angle for maximum light distribution

80 CRI - Ideal for general lighting applications

Technical Specifications

Product Type	Reflector
Bulb Shape	BR30
Wattage	9W
Wattage Equivalency	65W Incandescent
Typical Lumen Output	720
Efficacy	76 lm/W
Color Temperature	5000K Daylight
CRI	80
Base Type	E26
L70 Lifespan	25,000 hours
Operating Temperature	-20°C - 40°C
Dimmable	Yes, down to 10%
Beam Angle	110°
Warranty	3-Year, No-Compromise Warranty
For Use in Emergency Fixtures	No
For Use Outdoors in Open Fixtures	No


Electrical Characteristics

Input Voltage	120V
Power Factor	0.8
Flicker	<30%

Listings

UL Listed	Yes
ENERGY STAR V2.0	This product is ENERGY STAR® Version 2.0 Certified
Energy Star ID	2329313
CEC Status	Not lawful for sale in California

Light Distribution



Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	6	12	8	6.5
PALLET	840	47.9	40	39

Dimension

