

LBR30

PAR30 | LED LAMP

PROJECT _____

TYPE _____

- / 120 V
- / 50,000 Hours (L70)
- / Halogen PAR form factor (ANSI compliant)
- / Lightest LED lamps on the market
- / RoHS-compliant
- / Wet location rating
- / ETL Certified to UL Standard 1993
- / Contain no lead or mercury
- / Fully dimmable; Compatibility list available.
- / Base Types: E26 Standard; GU24*
- / Recommended for use in open environment fixtures
- / Approved for use in recessed IC and non-IC rated fixtures with open apertures only
- / 90+ High CRI standard



Weight: 6.6 oz.




Ordering Information

Example: LBR30/40/30h/WH

Lamp	Beam Spread	CCT	Color
LBR30	FL	25h*	WH - White
		27h	*SV - Silver
		30h	*BK - Black
		30m*	
		35h*	
		35m*	
		40h*	
		50h*	

Lamp	Product Code			Power (Watts)	CBCP (cd)	Standard CRI
	Beam Angle	CCT	Delivered Lumens			
LBR30	FL	25h	1000	14	2000	90
		27h	1100			
		30h				
		*30m				
		*35m				



*Consult factory for lead time and availability



OPTICS² involves a recessed primary optic and surface secondary optic that allows Solais LRP lamps to duplicate the exact performance and aesthetics of incandescents.



Thermal Throttle – In the event that Solais products begin to overheat, they will undetectably dim themselves to protect your technology investments.



Warranty



IES Files



Dimmers

WARNING: Not for use in fully enclosed luminaires. Risk of electric shock. Use in an indoor, dry location only. This device is not intended for use with emergency exit fixtures or emergency exit lights. May not be compatible with all dimmers; please visit solais.com/dimming for up-to-date dimmer compatibility information.

NOTES: This device complies with Part 15 of the FCC Rule. This product may cause interference with other devices. If interference occurs, change the locations of the products involved. **Compatible on 120v systems.**