



GE
Lighting

66468 - F32T8/25WSP41EC-T8-SPP NEW TECHNICAL LAMPS

F32T8/25W/SPP41/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	31.4
Rated Life Instant Start-Hrs	30000 h @ 3 h 36000 h @ 12 h
Rated Life Rapid Start - Hrs	40000 h @ 3 h 45000 h @ 12 h
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	40000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2350 lm
Nominal Initial Lumen per Watt	89
Initial Lumens-nominal	2500 lm
Color Rendering Index-CRI	80
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	66468
Description	F32T8/25W/SPP41/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168664684
Standard Package GTIN	10043168664681
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168664684

DIMENSIONS

Diameter	1.0 in
Nominal Length	48.0 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	25 W
---------------------	------