

Specification Sheet

BR30 Reflector Compact Fluorescent Lamp

Item Number 37970

Specifications

Energy Used (Watts)	15
Incandescent Equivalent Wattage	60
Domestic Code	15CFLBR30/F/27
Brightness (Lumens)	720
Average Rated Hours	10000
Life (in years)*	7.3
Light Appearance (Kelvin)	2700
CRI	80
CIE Chromaticity	x.459, y.412
Efficacy (LPW)	48
PF	≥0.5
Minimum Starting Temperature	0°F/-18°C
Estimated Yearly Energy Cost**	\$1.81
Country of Origin	China

Physical Characteristics


Finish	Warm White
Base	Medium (E26)
MOL	5 1/2"






Lumen Maintenance

Lumen Maintenance Curve



Spectral Distribution



Limited Warranty

This lamp is warranted to be free from defects in material and workmanship for 2 years (based on using 3 hours per day).

Do not for use with emergency exit luminaires or lights, photocontrols or electric timers. DO NOT USE WITH DIMMERS. Enclosed luminaire is required for outdoor use. Not for use in totally enclosed non-vented luminaires. NOTE: Product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

- * Based on 3 hrs./day
- * * Based on 3 hrs./day 11¢/kWh Cost depends on rates and use.



Contains mercury. (Hg) For more on clean up and safe disposal, visit epa.gov/CFL.

