


# Modular Wiring Devices

A revolutionary line of wiring devices  
engineered for fast and easy installation

## lev-lok®




# Simple, Secure Installation



## Install Wiring Module

- All modules have a Circuit ID Label for ease of identification
- Additional colors available for identifying emergency and isolated ground circuits




## Connect Wiring Device

- Simply push and twist to lock connection



## Finish Installation

- Install device into box
- Finish with wallplate





# lev-lok<sup>®</sup>

## Modular Wiring Devices

The perfect productivity solution for electrical construction and maintenance applications.

The ingenious Lev-Lok Modular Wiring Device System by Leviton simplifies the process of wiring device installation and replacement, resulting in streamlined construction projects that feature improved quality and profitability versus conventional wiring methods.

### Faster, Safer Installation

The Lev-Lok wiring module comes with pre-stripped wire leads, eliminating the need for making pigtails. With no exposed contacts, you can safely power up and test circuits at any time after the wiring modules are installed. And, device installation and replacement is up to 3 times faster than conventionally wired devices. A simple push and twist action securely fastens the wiring module to the device, providing a reliable and safe connection.

### Improved Quality

The Lev-Lok wiring device platform has been designed from the ground up to address the reliability and performance concerns of specification engineers without sacrificing the electrical contractor's need for fast, easy installation. The unique connection system prevents miswiring, ensuring that every device connection is correct, regardless of whether the installer is a first year apprentice, a seasoned journeyman or master electrician. The connection system is also much more intuitive than competitive products, greatly reducing the need for rework and/or callback after the job is complete.

### More Profitable

The combination of faster installation and improved quality allows contractors to complete jobs faster. This not only saves you money on each job, but allows you to bid and complete more jobs than would be possible with conventional device wiring. When replacing or upgrading the device, the process is just as quick and easy.










# Healthcare Facilities


## Extra Heavy Duty Hospital Grade Modular Wiring Devices

Leviton hospital grade modular receptacles and switches are found in healthcare facilities across the country. These devices are suitable for use in all 15A or 20A, 125V applications within healthcare facilities. Receptacles are offered in standard, tamper-resistant, power indication, illuminated and isolated ground versions of both our conventional and Decora Plus™ duplex configurations. We also offer a version specifically designed for use in MRI and other applications exposed to high magnetic fields. Switches are offered in standard toggle, tamper-resistant key toggle, illuminated toggle, and now, antimicrobial toggle versions. Ease of installation and change out is critical in healthcare environments. Lev-Lok wiring devices can be installed or changed out much quicker and safer than conventional wiring devices.



### Receptacle Features and Benefits:

- Nickel-plated brass single-piece, wrap-around mounting strap with integral ground contacts, for continuous conductivity and secure ground path
- Constructed with impact-resistant thermoplastic nylon, assuring durability of the device
- Extra heavy duty triple wipe “T” contacts provide superior plug retention force to meet the rugged plug demands found in healthcare environments
- Grounding clip permanently secured to strap makes for most reliable ground connection
- Smooth face prevents dirt from collecting and makes cleaning faster and simpler
- Four corner latches securely fasten the devices face to the body
- Wiring modules available in several colors for easy circuit identification: white (standard), red (for emergency circuits) and orange (for isolated ground circuits)
- Wiring modules are also available with UL Type XHHW-2 building wire for low leakage current applications



### Switch Features and Benefits:

- Heavy gauge galvanized steel mounting strap with self-grounding clip for reliable connection
- Color-coded covers: 15 Amp-Blue, 20 Amp-Red for easy circuit identification
- Available in single pole and three-way configurations
- Standard thermoplastic toggle has high-impact strength and withstands elevated operating temperatures
- Illuminated toggle provides easy switch visibility in dark environments
- Key-operated locking toggle provides tamper-resistant protection in public areas
- Antimicrobial treated toggle designed to reduce the growth of harmful bacteria on switch surface








# Educational Institutions


## Extra Heavy Duty Specification Grade Modular Wiring Devices

Leviton extra heavy duty specification grade modular receptacles and switches are manufactured with extremely durable components to withstand the rugged mechanical and electrical conditions of industrial environments. These devices are suitable for use in all 15A or 20A, 125V industrial installations. Receptacles are offered in standard, tamper-resistant, and isolated ground versions of both our conventional and Decora Plus™ duplex configurations. Switches are offered in standard toggle, tamper-resistant key toggle, illuminated toggle, and now, antimicrobial toggle versions. Leviton industrial grade modular wiring devices are an excellent choice for quick installation in locations that require frequent maintenance and replacement.



### Receptacle Features and Benefits:

- Solid brass single-piece, wrap-around mounting strap with integral ground contacts, for continuous conductivity and secure ground path
- Constructed with impact-resistant thermoplastic nylon, assuring durability of the device
- Grounding clip permanently secured to strap makes for most reliable ground connection
- Smooth face prevents dirt from collecting and makes cleaning faster and simpler
- Four corner latches securely fasten the devices face to the body
- Large triple-wipe “T” contacts for superior performance day-in and day-out
- Wiring modules available in several colors for easy circuit identification: white (standard), red (for emergency circuits) and orange (for isolated ground circuits)



### Switch Features and Benefits:

- Heavy gauge galvanized steel mounting strap with self-grounding clip for reliable connection
- Color-coded covers: 15 Amp-Blue, 20 Amp-Red for easy circuit identification
- Available in single pole and three-way configurations
- Standard thermoplastic toggle has high-impact strength and withstands elevated operating temperatures
- Illuminated toggle provides easy switch visibility in dark environments
- Key-operated locking toggle provides tamper-resistant protection in public areas
- Antimicrobial treated toggle designed to reduce the growth of harmful bacteria on switch surface








# Commercial Spaces


## Heavy Duty Specification Grade Modular Wiring Devices

Leviton heavy duty specification grade modular receptacles and switches are the perfect choice for commercial projects. Suitable for use in all 15A or 20A, 125V commercial applications, and backed by a limited 10-Year Warranty, these devices will satisfy the need for high quality and faster installation. Receptacles are offered in a wide variety of configurations, including standard and tamper-resistant versions of both our conventional and Decora Plus™ duplex configurations, and surge protective versions for point-of-use protection of computers and other office equipment. Switches are offered in standard toggle, tamper-resistant key toggle, illuminated toggle, and now, antimicrobial toggle versions. Lev-Lok commercial grade modular wiring devices will provide for quicker installation, yielding shorter project completion time lines while at the same time improving overall quality.



### Receptacle Features and Benefits:

- Galvanized steel single-piece, wrap-around mounting strap with riveted ground contacts provide for secure connections
- Constructed with impact-resistant thermoplastic nylon, assuring durability of the device
- Grounding clip permanently secured to strap makes for most reliable ground connection
- Smooth face prevents dirt from collecting and makes cleaning faster and simpler
- Four corner latches securely fasten the devices face to the body
- Tamper-resistant versions are equipped with a unique shutter system that prevents incidental contact with live contacts
- Large triple-wipe “T” contacts for superior performance day-in and day-out



### Switch Features and Benefits:

- Heavy gauge galvanized steel mounting strap with self-grounding clip for reliable connection
- Color-coded covers: 15 Amp-Blue, 20 Amp-Red for easy circuit identification
- Available in single pole and three-way configurations
- Standard thermoplastic toggle has high-impact strength and withstands elevated operating temperatures
- Illuminated toggle provides easy switch visibility in dark environments
- Key-operated locking toggle provides tamper-resistant protection in public areas
- Antimicrobial treated toggle designed to reduce the growth of harmful bacteria on switch surface

## Personnel Protection

### Extra Heavy Duty Industrial & Hospital Grade GFCI Modular Receptacles

Leviton extra heavy duty industrial and hospital grade GFCI modular receptacles are the perfect solution for those locations that require the added safety of ground fault protection, such as restrooms and kitchens. Suitable for use in all 15A or 20A, 125V commercial applications, these devices are offered in standard or tamper-resistant duplex receptacle versions. Designed to meet the latest UL standard for auto-monitoring (self-test), our complete line of self-test GFCI modular receptacles periodically conduct an automatic internal test to confirm that it can respond to a ground fault.



#### GFCI Receptacle Features and Benefits

- Advanced electronics offers superior resistance to surges and over-voltages
- Patented lockout feature prevents RESET if the GFCI is mis-wired or the circuit is no longer functioning properly
- Green LED indicator light indicates the presence of power to the receptacle
- Constructed with impact and chemical resistant PBT face, increasing durability to the device
- Brass self-grounding clip permanently staked on for secure and reliable performance
- Improved strap design provides greater support, even with ears removed
- Wraparound steel strap for superior durability in abusive environments
- Feed-through terminal screw covers provide added safety on unused terminals

## Energy Savings

### Wall Switch Occupancy Sensors

Leviton Wall Switch Occupancy Sensors are used to provide automatic lighting control for energy savings and convenience in a variety of commercial applications: private and executive offices, conference rooms, storage areas, restrooms, classrooms, lounges, training areas, etc. Available in Passive Infrared (PIR) and Multi-Technology (Ultrasonic and PIR) versions to accommodate a wide variety of spaces.





## Extra Heavy Duty Specification Grade Smooth Face Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	M5262	M5262-SG	M5362	M5362-SG
Ivory	M5262-I	M5262-SGI	M5362-I	M5362-SGI
White	M5262-W	M5262-SGW	M5362-W	M5362-SGW
Black	M5262-E	M5262-SGE	M5362-E	M5362-SGE
Blue	M5262-B	M5262-SGB	M5362-B	M5362-SGB
Gray	M5262-GY	M5262-SGG	M5362-GY	M5362-SGG
Red	M5262-R	M5262-SGR	M5362-R	M5362-SGR
Light Almond	M5262-T	M5262-SGT	M5362-T	M5362-SGT



## Extra Heavy Duty Specification Grade Isolated Ground Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Orange	M5262-IG	MT562-IG	M5362-IG	MT563-IG
Ivory	M5262-IGI	MT562-IGI	M5362-IGI	MT563-IGI
White	M5262-IGW	MT562-IGW	M5362-IGW	MT563-IGW
Black	M5262-IGE*	MT562-IGE*	M5362-IGE*	MT563-IGE*
Gray	M5262-IGG	MT562-IGG*	M5362-IGG	MT563-IGG*
Red	M5262-IGR	MT562-IGR	M5362-IGR*	MT563-IGR*
Light Almond	M5262-IGT*	MT562-IGT*	M5362-IGT*	MT563-IGT*

\*These colors are special order items - consult customer service for availability



## Extra Heavy Duty Specification Grade Isolated Ground, Decora Plus™ Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Orange	M1626-IG*	MT162-IG	M1636-IG*	MT163-IG*
Ivory	M1626-IGI*	MT162-IGI*	M1636-IGI*	MT163-IGI*
White	M1626-IGW*	MT162-IGW*	M1636-IGW*	MT163-IGW*
Black	M1626-IGE*	MT162-IGE*	M1636-IGE*	MT163-IGE*
Gray	M1626-IGG*	MT162-IGG*	M1636-IGG*	MT163-IGG*
Red	M1626-IGR*	MT162-IGR*	M1636-IGR*	MT163-IGR*
Light Almond	M1626-IGT*	MT162-IGT*	M1636-IGT*	MT163-IGT*

\*These colors are special order items - consult customer service for availability



## Extra Heavy Duty Industrial Grade SmartLockPRO® Self-Test GFCI Duplex Receptacles

Color	15A 125V 1HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	MGFN1	MGFT1	MGFN2	MGFT2
Ivory	MGFN1-I	MGFT1-I	MGFN2-I	MGFT2-I
White	MGFN1-W	MGFT1-W	MGFN2-W	MGFT2-W
Black	MGFN1-E	MGFT1-E	MGFN2-E	MGFT2-E
Gray	MGFN1-GY	MGFT1-GY	MGFN2-GY	MGFT2-GY
Red	MGFN1-R	MGFT1-R	MGFN2-R	MGFT2-R
Light Almond	MGFN1-T	MGFT1-T	MGFN2-T	MGFT2-T



## Heavy Duty Specification Grade Smooth Face Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	M5262-S	MT562-S	M5362-S	MT563-S
Ivory	M5262-SI	MT562-SI	M5362-SI	MT563-SI
White	M5262-SW	MT562-SW	M5362-SW	MT563-SW
Black	—	MT562-SE	—	MT563-SE
Blue	M5262-SB	MT562-SB	M5362-SB	MT563-SB
Gray	M5262-GYS	MT562-SGY	M5362-GYS	MT563-SGY
Red	M5262-SR	MT562-SR	M5362-SR	MT563-SR
Light Almond	M5262-ST	MT562-ST	M5362-ST	MT563-ST





## Heavy Duty Specification Grade Decora Plus™ Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	M1626	MT162	M1636	MT163
Ivory	M1626-I	MT162-I	M1636-I	MT163-I
White	M1626-W	MT162-W	M1636-W	MT163-W
Black	M1626-E	MT162-E	M1636-E	MT163-E
Blue	M1626-B	MT162-B	M1636-B	MT163-B
Gray	M1626-GY	MT162-GY	M1636-GY	MT163-GY
Red	M1626-R	MT162-R	M1636-R	MT163-R
Light Almond	M1626-T	MT162-T	M1636-T	MT163-T



## Heavy Duty Specification Grade Surge Protective Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Tamper-Resistant, with Indicator Light	Tamper-Resistant, with Indicator Light & Audible Alarm	Tamper-Resistant, with Indicator Light	Tamper-Resistant, with Indicator Light & Audible Alarm
Brown	MT528	MT728*	MT538	MT738*
Ivory	MT528-I	MT728-I	MT538-I	MT738-I
White	MT528-W	MT728-W	MT538-W	MT738-W
Black	MT528-E	MT728-E	MT538-E	MT738-E
Blue	MT528-B	MT728-B	MT538-B	MT738-B
Gray	MT528-GY	MT728-GY*	MT538-GY	MT738-GY*
Red	MT528-R*	MT728-R*	MT538-R*	MT738-R*
Light Almond	MT528-T	MT728-T	MT538-T*	MT738-T*

\*These colors are special order - contact customer service for availability



## Extra Heavy Duty Hospital Grade Smooth Face Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R			20A 125V 1HP, NEMA 5-20R		
	Standard	Tamper-Resistant	MRI* (Non-TR)	Standard	Tamper-Resistant	MRI* (Non-TR)
Brown	M8200	M8200-SG	—	M8300	M8300-SG	—
Ivory	M8200-I	M8200-SGI	MRI15-I	M8300-I	M8300-SGI	MRI20-I
White	M8200-W	M8200-SGW	MRI15-W	M8300-W	M8300-SGW	MRI20-W
Black	M8200-E	M8200-SGE	—	M8300-E	M8300-SGE	—
Blue	M8200-B	M8200-SGB	—	M8300-B	M8300-SGB	—
Gray	M8200-GY	M8200-SGG	MRI15-GY	M8300-GY	M8300-SGG	MRI20-GY
Red	M8200-R	M8200-SGR	MRI15-R	M8300-R	M8300-SGR	MRI20-R
Light Almond	M8200-T	M8200-SGT	MRI15-T	M8300-T	M8300-SGT	MRI20-T

\*MRI Series receptacles feature components made of non-ferrous metals that are safe for use in high magnetic field environments.



## Extra Heavy Duty Hospital Grade Smooth Face, Illuminated Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R			20A 125V 1HP, NEMA 5-20R		
	Illuminated	Illuminated, Tamper-Resistant	Power-Indication (Non-TR)	Illuminated	Illuminated, Tamper-Resistant	Power-Indication (Non-TR)
Ivory	M8200-ILI	MT820-ILI	M8200-PLI	M8300-ILI	MT830-ILI	M8300-PLI
White	M8200-ILW	MT820-ILW	M8200-PLW	M8300-ILW	MT830-ILW	M8300-PLW
Gray	M8200-ILG	MT820-ILG	M8200-PLG	M8300-ILG	MT830-ILG	M8300-PLG
Red	M8200-ILR	MT820-ILR	M8200-PLR	M8300-ILR	MT830-ILR	M8300-PLR
Light Almond	M8200-ILT	MT820-ILT	M8200-PLT	M8300-ILT	MT830-ILT	M8300-PLT



## Extra Heavy Duty Hospital Grade Isolated Ground Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Orange	M8200-IG	MT820-IG	M8300-IG	MT830-IG
Ivory	M8200-IGI	MT820-IGI	M8300-IGI	MT830-IGI
White	M8200-IGW	MT820-IGW	M8300-IGW	MT830-IGW
Black	M8200-IGE*	MT820-IGE*	M8300-IGE*	MT830-IGE*
Gray	M8200-IGG*	MT820-IGG*	M8300-IGG*	MT830-IGG*
Red	M8200-IGR	MT820-IGR	M8300-IGR	MT830-IGR
Light Almond	M8200-IGT*	MT820-IGT*	M8300-IGT*	MT830-IGT*

\*These colors are special order - contact customer service for availability



## Extra Heavy Duty Hospital Grade Decora Plus™ Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	M1626-HG0	—	M1636-HG0	—
Ivory	M1626-HGI	MT162-HGI	M1636-HGI	MT163-HGI
White	M1626-HGW	MT162-HGW	M1636-HGW	MT163-HGW
Black	M1626-HGE	—	M1636-HGE	—
Blue	M1626-HGB	—	M1636-HGB	—
Gray	M1626-HGG	MT162-HGG	M1636-HGG	MT163-HGG
Red	M1626-HGR	MT162-HGR	M1636-HGR	MT163-HGR
Light Almond	M1626-HGT	—	M1636-HGT	MT163-HGT



## Extra Heavy Duty Hospital Grade Decora Plus™ Illuminated Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R			20A 125V 1HP, NEMA 5-20R		
	Illuminated	Illuminated, Tamper-Resistant	Power Indication (Non-TR)	Illuminated	Illuminated, Tamper-Resistant	Power Indication (Non-TR)
Ivory	M1626-ILI*	MT162-ILI*	M1626-PLI	M1636-ILI*	MT163-ILI*	M1636-PLI
White	M1626-ILW	MT162-ILW	M1626-PLW	M1636-ILW	MT163-ILW	M1636-PLW
Gray	M1626-ILG*	MT162-ILG*	M1626-PLG	M1636-ILG*	MT163-ILG*	M1636-PLG
Red	M1626-ILR	MT162-ILR	M1626-PLR	M1636-ILR	MT163-ILR	M1636-PLR
Light Almond	M1626-ILT*	MT162-ILT*	M1626-PLT	M1636-ILT*	MT163-ILT*	M1636-PLT

\*These colors are special order - contact customer service for availability



## Extra Heavy Duty Hospital Grade Isolated Ground, Decora Plus™ Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Orange	MD820-IG	MDT82-IG	MD830-IG	MDT83-IG
Ivory	MD820-IGI	MDT82-IGI	MD830-IGI*	MDT83-IGI
White	MD820-IGW	MDT82-IGW	MD830-IGW	MDT83-IGW
Black	MD820-IGE*	MDT82-IGE	MD830-IGE*	MDT83-IGE
Gray	MD820-IGG*	MDT82-IGG	MD830-IGG*	MDT83-IGG*
Red	MD820-IGR	MDT82-IGR	MD830-IGR	MDT83-IGR*
Light Almond	MD820-IGT*	MDT82-IGT	MD830-IGT*	MDT83-IGT

\*These colors are special order - contact customer service for availability



## Extra Heavy Duty Hospital Grade SmartLockPRO® Self-Test GFCI Duplex Receptacles

Color	15A 125V 1HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	MGFN1-HG	MGFT1-HG	MGFN2-HG	MGFT2-HG
Ivory	MGFN1-HGI	MGFT1-HGI	MGFN2-HGI	MGFT2-HGI
White	MGFN1-HGW	MGFT1-HGW	MGFN2-HGW	MGFT2-HGW
Black	MGFN1-HGE	MGFT1-HGE	MGFN2-HGE	MGFT2-HGE
Gray	MGFN1-HGG	MGFT1-HGG	MGFN2-HGG	MGFT2-HGG
Red	MGFN1-HGR	MGFT1-HGR	MGFN2-HGR	MGFT2-HGR
Light Almond	MGFN1-HGT	MGFT1-HGT	MGFN2-HGT	MGFT2-HGT



## Heavy Duty Hospital Grade Smooth Face Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
	Standard	Tamper-Resistant	Standard	Tamper-Resistant
Brown	M8200-H	MT820	M8300-H	MT830
Ivory	M8200-HI	MT820-I	M8300-HI	MT830-I
White	M8200-HW	MT820-W	M8300-HW	MT830-W
Black	M8200-HE	MT820-E	M8300-HE	MT830-E
Blue	M8200-HB	MT820-B	M8300-HB	MT830-B
Gray	M8200-HGY	MT820-GY	M8300-HGY	MT830-GY
Red	M8200-HR	MT820-R	M8300-HR	MT830-R
Light Almond	M8200-HT	MT820-T	M8300-HT	MT830-T





## Heavy Duty Hospital Grade Surge Protective Duplex Receptacles

Color	15A 125V 1/2HP, NEMA 5-15R	20A 125V 1HP, NEMA 5-20R
	Indicator Light & Audible Alarm	Indicator Light & Audible Alarm
Brown	MT828*	MT838
Ivory	MT828-I	MT838-I
White	MT828-W	MT838-W
Black	MT828-E*	MT838-E*
Blue	MT828-B	MT838-B
Gray	MT828-GY*	MT838-GY
Red	MT828-R	MT838-R
Light Almond	MT828-T	MT838-T*

\*These colors are special order - contact customer service for availability



## Extra Heavy Duty Specification Grade Single Pole Toggle Switches

Color	15A 120V 1/2HP	15A 240V 2HP	15A 120V 1/2HP
	Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle
Brown	M1201	M1201-L	M1201-LHC (Clear)
Ivory	M1201-I	M1201-IL	M1201-LHI
White	M1201-W	—	M1201-LHW
Black	—	—	—
Gray	M1201-GY	—	—
Red	M1201-R	—	—
Light Almond	—	—	—



AM120-W shown with 84001-A40 Wallplate (sold separately)

Color	20A 120V 1HP	20A 240V 2HP	20A 120V 1HP	20A 120/277V 1HP
	Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle	Antimicrobial Treated Toggle*
Brown	M1221	M1221-L	M1221-LHC (Clear)	—
Ivory	M1221-I	M1221-IL	M1221-LHI	AM120-I
White	M1221-W	M1221-WL	M1221-LHW	AM120-W
Black	M1221-E	—	—	—
Gray	M1221-GY	M1221-GL	—	AM120-GY
Red	M1221-R	M1221-RL	—	AM120-R
Light Almond	M1221-T	—	—	—

\* When used with antimicrobial treated wallplates provides a complete antimicrobial solution. Visit [www.leviton.com/antimicrobial](http://www.leviton.com/antimicrobial) for more information.

## Extra Heavy Duty Specification Grade 3-Way Toggle Switches

Color	15A 120V 1/2HP, 240V 2HP	15A 120V 1/2HP, 240V 2HP	15A 120V 1/2HP
	Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle
Brown	M1203	M1203-L	M1203-LHC (Clear)
Ivory	M1203-I	M1203-IL	M1203-LHI
White	M1203-W	—	M1203-LHW
Black	—	—	—
Gray	M1203-GY	—	—
Red	M1203-R	—	—
Light Almond	—	—	—

Color	20A 120V 1HP, 240V 2HP	20A 120V 1HP, 240V 2HP	20A 120V 1HP	20A 120/277V 1HP
	Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle	Antimicrobial Treated Toggle*
Brown	M1223	M1223-L	M1223-LHC (Clear)	—
Ivory	M1223-I	M1223-IL	M1223-LHI	AM320-I
White	M1223-W	M1223-WL	M1223-LHW	AM320-W
Black	M1223-E	—	—	—
Gray	M1223-GY	M1223-GL	—	AM320-GY
Red	M1223-R	M1223-RL	—	AM320-R
Light Almond	M1223-T	—	—	—

\* When used with antimicrobial treated wallplates provides a complete antimicrobial solution. Visit [www.leviton.com/antimicrobial](http://www.leviton.com/antimicrobial) for more information.



## PIR and Multi-Technology Decora® Wall Switch Occupancy Sensors

Color	PIR	PIR with Self-Adaptive Technology	Multi-Technology
Ivory	MDS10-IDI	MDS15-IDI	MSSMT-GDI
White	MDS10-IDW	MDS15-IDW	MSSMT-GDW
Black	MDS10-IDE	MDS15-IDE	MSSMT-GDE
Gray	MDS10-IDG	MDS15-IDG	MSSMT-GDG
Light Almond	MDS10-IDT	MDS15-IDT	MSSMT-GDT



## Wiring Modules



Lev-Lok Receptacle Modules, 20A, 125V	Module Color	Wire Type	Wire Colors	Cat No
Stranded Wire Leads	White	THHN	Black, White, Green	MSTWL-A
Stranded Wire Leads with Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WST
Stranded Wire Leads for Emergency Circuits	Red	THHN	Black, White, Green	MSTWL-R
Stranded Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-IG
Stranded Wire Leads with Push Wire Connectors for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-WIG
Solid Wire Leads	White	THHN	Black, White, Green	MSTWL-SDA
Solid Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-SIG
Solid Wire Leads with Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WSD
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Orange, Brown, Green/Yellow	MSTWL-XA*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Brown/Yellow, Orange/Blue, Green/Yellow	MSTWL-XI*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Black, White, Green/Yellow	MSTWL-XN*
Lev-Lok Single Pole Switch Modules, 20A, 347V				
Stranded Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-ST
Stranded Wire Leads with Push Wire Connectors	Yellow	THHN	Black, Black, Green	MSPSW-WST
Solid Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-SD
Stranded Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7ST
Solid Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7SD
Lev-Lok 3-Way Switch Modules, 20A, 347V				
Stranded Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-ST
Stranded Wire Leads with Push Wire Connectors	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-WST
Stranded Wire Leads for 277V Lighting Applications	Yellow	XHHW-2	Brown, Yellow, Yellow, Green	M3WSW-7ST
Solid Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-SD
Lev-Lok Occupancy Sensor Modules, 20A, 347V				
Stranded Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XST
Solid Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XSD


\*add suffix of 0 for 6", 1 for 12", 2 for 24" or 3 for 36" long leads; please allow 4 to 6 weeks for delivery

## Lev-Lok Circuit Analyzer

	Cat No
Circuit Analyzer for Lev-Lok Receptacle Modules (MSTWL)	LVLOK-TST



# NEW Lev-Lok® Circuit Analyzer



The Lev-Lok Circuit Analyzer helps in testing the circuit prior to installing Lev-Lok Receptacles. Simply insert the tester into a Leviton Lev-Lok receptacle wiring module and you will be able to confirm the status of the circuit right away.

- Easy to read indicator lights reveal 5 common wiring issues:
  - Open hot
  - Open ground
  - Open neutral
  - Hot/ground reverse
  - Hot/neutral reverse
- Compact ergonomic design includes comfort grip for an easy-to-use user experience
- Convenient built-in keyhole for lanyard attachment
- cCSAus Listed

## Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747  
Phone: 1-800-323-8920 • FAX: 1-800-832-9538  
Tech Line (8:30AM-7:00PM E.S.T. Mon-Fri): 1-800-824-3005

## Leviton Manufacturing of Canada, Ltd.

165 Hymus Blvd, Pointe-Claire, QC H9R 1E9  
Telephone: 1-800-469-7890 • FAX: 1-800-563-1853

## Leviton S. de R.L. de C.V.

Lago Tana 43, Col. Huichapan, Miguel Hidalgo, CP 11290 México DF  
Tel. (+52) 55-5082-1040 • Fax: (+52) 55-5386-1797 • [www.leviton.com.mx](http://www.leviton.com.mx)

Visit us on the web at: [www.leviton.com/commercial](http://www.leviton.com/commercial) • email: [commercial@leviton.com](mailto:commercial@leviton.com)