

FLEXTRAY™

FLX-15

B-LINE
SERIES

FLEXTRAY™ wire basket



EATON

Powering Business Worldwide



Energizing a world that demands more.

We deliver:

- **Electrical solutions** that use less energy, improve power reliability and make the places we live and work safer and more comfortable
- **Hydraulic and electrical solutions** that enable machines to deliver more productivity without wasting power
- **Aerospace solutions** that make aircraft lighter, safer and less costly to operate, and help airports operate more efficiently
- **Vehicle drivetrain and powertrain solutions** that deliver more power to cars, trucks and buses, while reducing fuel consumption and emissions

Discover today's Eaton.

Powering business worldwide

As a global power management company, we help customers worldwide manage the power needed for buildings, aircraft, trucks, cars, machinery and businesses.

Eaton's innovative technologies help customers manage electrical, hydraulic and mechanical power more reliably, efficiently, safely and sustainably.

We provide integrated solutions that help make energy, in all its forms, more practical and accessible.











With 2014 sales of \$22.6 billion, Eaton has approximately 100,000 employees around the world and sells products in more than 175 countries.



Eaton.com

EATON

Powering Business Worldwide

Table of Contents

Introduction	2 & 3	
Technical Data		
Finishes	4	
Load & Fill Charts	5	
Straight Sections		
1½" & 2" Deep FLEXTRAY	6	
4" & 6" Deep FLEXTRAY	7	
Splicing Accessories		
Washer Splice Kit, Splice hardware Components, Connecting Hardware, Wing Splice™, Splice Plates, FLEXMATE System	9 - 11	
Tab-Loc Connector, Splice & Expansion Bars	12 - 14	
Hold Down Plate, Horizontal Adjustable Kit, 90° Kit,	15	
Splice Plate Kits	16 & 17	
Ceiling Support Methods		
Flip Clip™, Trapeze Supports	19	
2" Center Hanger, Hold Down Clamp, Mounting Bracket	20	
Center Hung Clip, Threaded Rod Protector	21	
Center Trapeze Hanger, KwikWire™, KwikPak™	22 - 25	
Wall Support Methods		
Shelf Brackets, L Brackets, Z Brackets, Hold Down Clamp	27 & 28	
Attachment Clips, Mounting Bracket, Wall Supports	29	
Wall Termination Kit, Wall Mount Kit, C Brackets	30 & 31	
F.A.S.T.™ System		
FLEXTRAY, Stands, Cantilever Kits	33 - 35	
Hold Down & Pedestal Clips, Cantilever Foot, Under Floor Stand, L Bracket & Toolless Clip, Pedestal Clamp & Kit	36 & 37	
Under Floor Bracket, U-Bolts, Ground Bolt, Adhesive Feet, Floor Stand	38 & 39	
Accessories		
Covers, Dividers, Inserts, Blind Ends	41 & 42	
Cable Roller, Toolless Clip, Mounting Clip	43	
Drop Outs, Conduct Connector, Rack Clamp, Adaptor Clip	44 & 45	
Radius Sheet, Rubber Caps, Touch-Up Paint, Label Clip, Ground Bolt, Ground Wire Support	46 & 47	
Threaded Rod, Nuts, Washers, Beam Clamps, Spring Nuts, Bolted Framing, Rapid Rod Hangers	48 & 49	
Installation		
FLEXTRAY Cutters & Benders	51 & 52	
Cutting Diagrams for Horizontal Bends, Reducers, Vertical Inside & Outside Bends, Tees, Crosses	53 - 57	
Index	58 - 59	





Flextray is a flexible, field-adaptable way to manage cables throughout a project. The tray can be cut and bent to the needs of the installer on the jobsite, allowing cable runs to be adjusted as needed. The wide range of sizes makes Flextray a great choice for small cable drops a large trunk of cables. The tray has the market-preferred "T" weld safety edge, protecting both the cable and the installer during cable installation. Flextray is also UL Classified as an equipment grounding conductor.

The F.A.S.T.™ System is Foldable, Adjustable, Stackable, and Tool-less, providing many options to manage cables inside your raised floor space. With only a few parts, you can create a basic single layer installation to a cantilevered, multiple-tier cable run. Make the most of your raised floor space and your time with the F.A.S.T. System.

Finish Information

Flextray Cable Tray and Accessories are available in a wide variety of finishes to meet the environmental or aesthetic requirements of customer installations. Use the list below to find the finish and suffix that will meet your needs. Available product finishes will be listed on individual pages throughout the catalog. Finish codes shown in bold type are the standard for that product.

Plain wire: ASTM A510, Grade 1008

EG Electroplated Zinc Galvanized Finish applied after fabrication
(ELG) Recommended applications: Controlled interior
UL/CSA Classified as an equipment ground conductor when spliced as recommended
ASTM B633 - Average thickness of 0.3 mils (8 microns)

GS Pre-Galvanized Zinc Finish applied before fabrication
(GLV) Recommended applications: Limited industrial & interior
UL/CSA Classified as an equipment ground conductor when spliced as recommended
ASTM A641

BLE Black Powder Coat Finish applied after fabrication
Recommended applications: Controlled interior
UL/CSA Classified as an equipment ground conductor when coating has been removed at splice contact points
Average paint thickness of 1.2 mils (30 microns) to 3.0 mils (75 microns)

HD Hot Dip Galvanized Finish applied after fabrication
(HDG) Recommended applications: Exterior, corrosive. Not intended for clean room applications.
UL/CSA Classified as an equipment ground conductor when spliced as recommended
ASTM A123 - Average thickness of 2.4 mils (60 microns) to 3.2 mils (80 microns)

304S 304L Stainless Steel
(SS4) Recommended applications: Food preparation, wash-down areas
ASTM A580

316S 316L Stainless Steel
(SS6) Recommended applications: Highly corrosive applications & marine environments
ASTM A580

Custom Powder Coat Finish applied after fabrication
Recommended applications: Controlled interior
UL/CSA Classified as an equipment ground conductor when coating has been removed at splice contact points
No Specification

Grounding Information

Statement for all UL Classified products:



This product is classified by Underwriters Laboratories, Inc. as to its suitability as an equipment grounding conductor only. 556E



Most sizes of FLEXTRAY are UL Classified to serve as an Equipment Ground Conductor. The ground path can be achieved in one of two ways listed on page FLX-5:

Grounding Information (cont.)

1. Use the recommended quantity of UL Classified splices to connect sections and at places where the tray is cut.
2. Run an appropriately sized ground wire alongside the tray and attach it to each tray section and on both sides of a cut in the tray. (This method is recommended by NEMA VE-2 Installation Manual.)

Load & Fill Chart

Technical Data


FLEXTRAY Series Part Number	Size height x width	Support Span / Loading Capacity*				Cable Fill (50% fill)**		
		5'-0"	6'-0"	7'-0"	8'-0"	Actual Area Inside Tray (in ²)	Number of CAT 5e Cables***	Number of CAT 6 Cables***
FT1.5X12	1 1/2" x 12"	29	17	14	11	12.2	176	124
FT2X2	2" x 2"	34	28	24	20	4.3	61	43
FT2X4	2" x 4"	52	43	35	27	8.2	118	83
FT2X6	2" x 6"	66	47	35	27	12.1	175	123
FT2X8	2" x 8"	66	47	35	27	16.1	231	163
FT2X12	2" x 12"	68	47	35	27	23.9	345	243
FT2X16	2" x 16"	68	47	35	27	31.8	459	324
FT2X18	2" x 18"	68	47	35	27	35.8	516	364
FT2X20	2" x 20"	68	47	35	27	39.7	573	404
FT2X24	2" x 24"	68	47	35	27	47.5	686	484
FT2X30	2" x 30"	68	47	35	27	59.8	862	608
FT2X32	2" x 32"	77	53	39	30	63.3	914	645
FT4X4	4" x 4"	58	49	42	36	15.8	227	160
FT4X6	4" x 6"	93	77	60	46	23.6	341	240
FT4X8	4" x 8"	94	78	61	47	31.5	454	321
FT4X12	4" x 12"	119	83	61	47	47.5	686	484
FT4X16	4" x 16"	119	83	61	47	63.5	917	647
FT4X18	4" x 18"	119	83	61	47	71.5	1032	728
FT4X20	4" x 20"	119	83	61	47	79.5	1148	810
FT4X24	4" x 24"	128	89	65	50	95.5	1379	973
FT4X30	4" x 30"	128	89	65	50	119.5	1725	1217
FT6X8	6" x 8"	111	77	57	43	47.3	682	481
FT6X12	6" x 12"	124	86	63	48	71.6	1034	729
FT6X16	6" x 16"	128	89	65	50	95.3	1375	970
FT6X18	6" x 18"	128	89	65	50	107.3	1549	1092
FT6X20	6" x 20"	141	98	72	55	118.9	1716	1211
FT6X24	6" x 24"	154	107	78	60	143.3	2068	1459

* Published load chart has not been tested with Flexmate splice. Please consult the factory for load information when using the Flexmate option.


** FLEXTRAY fill capacity is based on NEC allowable fill of 50%. The NEC rule requires that the cable cross-sectional areas together may not exceed 50% of the tray area (width x depth = fill). Cables will nearly completely fill the cable tray when reaching the 50% cable fill, due to empty space between the surface of the cables. TIA recommends 40% fill ratio. Flextray loads shown in the loading chart will not be exceeded at 50% fill.

*** CAT 5e 4-pr non-plenum approximated at .21 in. diameter, CAT 6 4-pr non-plenum approximated at .25 in. diameter. Actual diameters vary by cable manufacturer.

1.5" Deep FLEXTRAY



Height: 1.38" (35 mm)
Length: 118.312" (3 meter)
Wire Dia. Minimum: .196" (5.0 mm)
Finishes:
 EG, GS, BLE, HD, 304S, 316S





Part Number	Width		Wt. Per Pc.	
	in.	mm	lbs.	kg
FT1.5X4X10	4"	100	5.8	2.63
FT1.5X6X10	6"	150	7.4	3.35
FT1.5X8X10	8"	200	9.0	4.08
FT1.5X12X10	12"	300	12.1	5.49


Only FT1.5X12 (12" wide) is UL Classified

Straight Sections

2" Deep FLEXTRAY



Height: 2.38" (60 mm)
Length: 118.312" (3 meter)
Wire Dia. Minimum: .196" (5.0 mm)
Finishes:
 EG, GS, BLE, HD, 304S, 316S



Part Number	Width		Wt. Per Pc.	
	in.	mm	lbs.	kg
FT2X2X10	2"	50	6.6	2.99
FT2X4X10	4"	100	8.2	3.72
FT2X6X10	6"	150	9.7	4.40
FT2X8X10	8"	200	11.2	5.08
FT2X12X10	12"	300	14.3	6.48
FT2X16X10	16"	400	17.4	7.89
FT2X18X10	18"	450	18.9	8.57
FT2X20X10	20"	500	20.4	9.25
FT2X24X10	24"	600	23.5	10.66
FT2X30X10	30"	750	28.1	12.74
FT2X32X10	32"	800	29.7	13.47


FT2X6 (6" wide) through FT2X32 (32" wide) are UL Classified

See page 4 for finish information

4" Deep FLEXTRAY

Part Number	Width		Wt. Per Pc.	
	in.	mm	lbs.	kg
FT4X4X10	4"	100	11.25	5.10
FT4X6X10	6"	150	12.79	5.80
FT4X8X10	8"	200	14.32	6.49
FT4X12X10	12"	300	17.39	7.89
FT4X16X10	16"	400	20.45	9.27
FT4X18X10	18"	450	21.99	9.97
FT4X20X10	20"	500	23.52	10.67
FT4X24X10	24"	600	26.59	12.06
FT4X30X10	30"	750	31.19	14.15

All 4" deep Flextrays are UL Classified




Height: 4.38" (111 mm)
Length: 118.312" (3 meter)
Wire Diameter Minimum: .196" (5.0 mm)
Finishes: EG, GS, BLE, HD, 304S, 316S

6" Deep FLEXTRAY


Part Number	Width		Wt. Per Pc.	
	in.	mm	lbs.	kg
FT6X8X10	8"	200	17.39	7.89
FT6X12X10	12"	300	20.45	9.27
FT6X16X10	16"	400	23.52	10.67
FT6X18X10	18"	450	25.06	11.37
FT6X20X10	20"	500	26.59	12.06
FT6X24X10	24"	600	29.66	13.45

All 6" deep Flextrays are UL Classified



Height: 6.38" (162 mm)
Length: 118.312" (3 meter)
Wire Diameter Minimum: .196" (5.0 mm)
Finishes: EG, GS, BLE, HD, 304S, 316S

See page 4 for finish information



Splicing Accessories


Washer Splice Kit

- Washer is staked to bolt, holding part stationary during installation
- Fewer parts to handle
- For use with all tray widths and sizes
- Finishes __: **EG, BLE**

BLE suffix indicates black zinc finish for this part only



Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
WASHER SPL KIT__	Assembly of Staked Washer Stud/Washer & Finned Nut	100	4.5	2.04



Splicing Chart (number of splices required for UL Classification)

Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	4	4	4	4	4	5	5
4"	NM	4	5	6	6	7	7	7	8
6"	NM	NM	NM	6	6	7	7	7	8

NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size

Splice Hardware Components


- Works with all splicing needs
- For use with all tray widths and sizes
- Components are sold separately
- Finishes __: **EG, BLE-BLO, 304S, 316S**

FTHDWE 1/4 not available in **BLE**.

TOP WASHER & BTM WASHER not available in **BLO**.



Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FTHDWE 1/4__	1/4" x 1" Carriage Bolt & Finned nut	100	1.2	0.54
TOP WASHER__	1" Square Splice Washer	100	1.4	0.63
BTM WASHER__	1 3/16" Square Splice Washer	100	2.0	0.91



BTM WASHER



FTHDWE1/4



TOP WASHER

Splicing Chart (number of splices required for UL Classification)


Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	4	4	4	4	4	5	5
4"	NM	4	5	6	6	7	7	7	8
6"	NM	NM	NM	6	6	7	7	7	8

NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size


See page 4 for finish and grounding information

Connecting Hardware

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FTSCH__	Connecting Hardware	50	2.0	0.91



- Adaptable and designed for use with splice plate (FTS3SP), SPLICE BAR, and long splice bar (FTS36SB).
- Finishes __: EG, BLE-BLO, 304S, 316S



Splicing Chart (number of splices required for UL Classification)

Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	4	4	4	4	4	5	5
4"	NM	4	5	6	6	7	7	7	8
6"	NM	NM	NM	6	6	7	7	7	8


NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size

Wing Splice™

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FTSWN__	Wing Splice	50	3.0	1.38



- Two piece design for easy handling
- Tool-less installation
- Reduces installation time, especially when used on fittings and bends
- Finish__: ZN



Splicing Chart (number of splices required for UL Classification)

Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	4	4	4	4	4	5	5
4"	NM	4	5	6	6	7	7	7	8
6"	NM	NM	NM	6	6	7	7	7	8


NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size

See page 4 for finish and grounding information

Splice Plate (only)

Part Number	Description	Length		Height		Hole Diameter		Qty./Box	Wt./Box	
		in.	mm	in.	mm	in.	mm		lbs.	kg
FTS3SP__	Splice Plate	2.7"	68.5	1.6"	40.6	0.27"	6.8	50	6.1	2.76

- Splice plate is designed for use with connecting hardware (FTSCH) to provide added stability of splice connections
- Hardware sold separately
- Finish__: **ZN**, SS6
- Note: FT2x2x10 and FT2x4x10 are not UL Classified



FLEXMATE™ Splice System

- Fastest splice connection method available in the industry
- For use with 4" (100mm) to 12" (300mm) wide tray
- FLEXMATE clips and tool sold separately
- Finishes __: **GS**, BLE

Note: Please contact us when using Flexmates on tray widths larger than 12" (300mm) for specific requirements.
We recommend that splice/supports comply with NEMA VE-2 installation requirements


Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FLEXMATE2__	Flexmate Splice Clips	100	1.0	0.45
FLEXMATE TOOL	Flexmate Splice Tool	1	0.7	0.32



FLEXMATE TOOL

Flexmate Tool is used to install splices quickly.

Position clip inside tool, pointing to outside of tray.



Squeeze to secure splice.

Splicing Chart (number of splices required for UL Classification)

Tray Height	Tray Width - number of splices				
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)
2"	2	2	4	4	4
4"	NM	4	5	6	6
6"	NM	NM	NM	6	6

NC = Not UL Classified in this size

NM = FLEXTRAY is not manufactured in this size

See page 4 for finish and grounding information

Tab-Loc Connector


Part Number	Description	Length		Qty./Box	Wt./Box	
		in.	mm		lbs.	kg
FTSTLC__	Tab-Loc Connectors	9.29"	235.9	50	7.2	3.26



- Fast splice for straight runs of tray
- For use with 2" (50mm) to 32" (800mm) wide tray to connect straight sections only
- Finishes __: **ZN**, SS6

Application Requirements




The recommendations listed are equal for all depths (except as noted).



Splicing Chart (number of splices required for UL Classification)


Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	2	2	4	4	4	4	4	5	5
4"	NM	4	5	6	6	7	7	7	8
6"	NM	NM	NM	6	6	7	7	7	8

NM = FLEXTRAY is not manufactured in this size



Tab-Loc security without special tools.

Screwdriver can also be used to bend tab-locs (hold connector ends while bending).




See page 4 for finish and grounding information


Splice Bar

- Adds rigidity to washer splice methods
- Used on side rails only (not for use in tray bottom)
- For use on trays when using splice hardware FTSCHE
- Hardware sold separately
- Finishes __: **EG**, BLE, HD, 304S, 316S

Part Number	Bar Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
SPLICE BAR __	10 ¹³ / ₁₆ "	274.6	50	14.0	6.35



Hardware is not sold with splice bar.



Each splice bar requires three (3) each of Hardware Splice Components - TOP WASHER, and FTSDWE 1/4 to complete connection. These items must be ordered separately.

Washer Splice Kits (WASHER SPL KIT) are required for connections on bottom of tray.

Splicing Chart (number of splices required for UL Classification)

Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	2	2	2	2	2	2	2
4"	NM	4	4	4	4	4	4	4	4
6"	NM	NM	NM	4	4	4	4	4	4


NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size

See page 4 for finish and grounding information

Splice Bar Kit

Part Number	Bar Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTSBK__	12"	304.8	5 Sets	6.4	2.90

- Adds rigidity
- Includes two (2) SPLICE BAR and hardware
- Finishes __: **ZN**, FB, SS6



Splicing Chart (number of splices required for UL Classification)


Tray Height	Tray Width - number of splices								
	2" (50mm)	4" (100mm)	6" (150mm)	8" (200mm)	12" (300mm)	16" (400mm)	18" (450mm)	20" (500mm)	24" (600mm)
2"	NC	NC	2	2	2	2	2	2	2
4"	NM	4	4	4	4	4	4	4	4
6"	NM	NM	NM	4	4	4	4	4	4

NC = Not UL Classified in this size NM = FLEXTRAY is not manufactured in this size

Expansion Splice Kit

Part Number	Bar Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTS12ESK__	12"	304.8	1 Kit	0.45	0.20

- Allows 1³/₄" (44mm) of expansion between two pieces of Flextray at expansion joints.
- To install, tighten nylon loc-nut until nut comes into contact with splice bar, then loosen approximately 1/4 turn.
- Includes two (2) splice bars and eight (8) sets of hardware
- Finishes __: **ZN**



Long Splice Bar (only)

Part Number	Bar Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTS12SB__	12"	304.8	1	0.13	0.06
FTS36SB__	36"	914.4	1	0.40	0.18

- FTS36SB long splice bar is used for assembly of large radius horizontal bends or field cut into short splice bars
- Splice Bars are designed for use with connecting hardware (FTSCH)
- Hardware sold separately
- Finishes __: **ZN**, FB, SS6



FTS12SB - 6 slots


FTS36SB - 18 slots

See page 4 for finish and grounding information

Hold Down Plate

- Easy way to mount 4" (100mm) wide tray for raceway run.
- Use 1/4" screws to attach SUPT WASHER to your specific wall/stud application (hardware sold separately).
- FTA6HD can be used in pairs to create a center-hung support using 3/8" rod.
- To protect cables use threaded rod protector (page 21).
- To complete 3/8" center hanger assembly use:
 - 2 - FTA6HD
 - 2 - HN 3/8"-16 hex nuts
- Finish: **ZN**, SS6


Part Number	Description	Qty./Box	Wt./Box lbs. kg
SUPT WASHER__	.28" x .70" 7.1mm x 17.8mm	50	4.7 2.13
FTA6HD__	.40" x .70" 10.1mm x 17.8mm	50	3.5 1.59



- Horizontal adjustable kit can be used to create horizontal angles from prepared FLEXTRAY straight sections
- Conveniently poly-bagged
- Finishes __: **EG**, BLE, 316S

Horizontal Adjustable Kit


Part Number	Description	Qty./Box	Wt./Box lbs. kg
FTSHAK__	Horizontal Adjustable Kit	10	2.4 1.09



- For fast assembly of 90° turns and tee fittings
- For use with all tray widths and sizes
- One kit will make two 90° turns or one tee fitting
- 90 DEGREE KIT: includes: two (2) 90° splice bars and eight (8) FTSCH
- Finishes __: **EG**, BLE, 316S

90 Degree Kit





Part Number	Description	Qty./Box	Wt./Box lbs. kg
90 DEGREE KIT__	90 degree splice bar & hardware	1	1.3 0.59



See page 4 for finish and grounding information


FLEXTRAY™ - Splicing Accessories

Components Required to Connect Two Sections of FLEXTRAY

System Part Number	System Width in. mm	Connector Assembly WASHER SPL KIT	Connecting Hardware FTSCH	Splice Plate FTS3SP	Splice Bar SPLICE BAR
					
FT2X2	2" 50	2	-	-	-
FT2X4	4" 100	2	-	-	-
FT2X6	6" 150	4 ¹	-	-	-
FT2X8	8" 200	4 ¹	-	-	-
FT2X12	12" 300	4 ¹	-	-	-
FT2X16	16" 400	4 ¹	-	-	-
FT2X18	18" 450	4 ¹	-	-	-
FT2X20	20" 500	5 ¹	-	-	-
FT2X24	24" 600	5 ¹	-	-	-
FT2X30	30" 750	7 ¹	-	-	-
FT2X32	32" 800	7 ¹	-	-	-
FT4X4	4" 100	4 ¹	-	-	-
FT4X6	6" 150	5 ¹	-	-	-
FT4X8	8" 200	6 ²	-	-	-
FT(*)X12	12" 300	6 ²	-	-	-
FT(*)X16	16" 400	7 ²	-	-	-
FT(*)X18	18" 450	7 ²	-	-	-
FT(*)X20	20" 500	7 ²	-	-	-
FT(*)X24	24" 600	8 ²	-	-	-
FT(*)X30	30" 750	8 ²	-	-	-
FT2X2	2" 50	-	2	2	-
FT2X4	4" 100	-	2	2	-
FT2X6	6" 150	1	2	2	-
FT2X8	8" 200	1	2	2	-
FT2X12	12" 300	2	2	2	-
FT2X16	16" 400	2	2	2	-
FT2X18	18" 450	2	2	2	-
FT2X20	20" 500	2	2	2	-
FT2X24	24" 600	2	2	2	-
FT2X30	30" 750	4	2	2	-
FT2X32	32" 800	4	2	2	-
FT4X4	4" 100	1	2	2	-
FT4X6	6" 150	2	2	2	-
FT4X8	8" 200	2	2	2	-
FT(*)X12	12" 300	3	2	2	-
FT(*)X16	16" 400	4	2	2	-
FT(*)X18	18" 450	4	2	2	-
FT(*)X20	20" 500	4	2	2	-
FT(*)X24	24" 600	4	2	2	-
FT(*)X30	30" 750	5	2	2	-
FT2X2	2" 50	-	2	-	2
FT2X4	4" 100	-	2	-	2
FT2X6	6" 150	1	2	-	2
FT2X8	8" 200	1	2	-	2
FT2X12	12" 300	2	2	-	2
FT2X16	16" 400	2	2	-	2
FT2X18	18" 450	2	2	-	2
FT2X20	21" 500	2	2	-	2
FT2X24	24" 600	2	2	-	2
FT2X30	30" 750	3	6	-	2
FT2X32	32" 800	3	6	-	2
FT4X4	4" 100	1	2	-	2
FT4X6	6" 150	2	2	-	2
FT4X8	8" 200	2	6	-	2
FT(*)X12	12" 300	2	6	-	2
FT(*)X16	16" 400	3	6	-	2
FT(*)X18	18" 450	3	6	-	2
FT(*)X20	20" 500	3	6	-	2
FT(*)X24	24" 600	3	6	-	2
FT(*)X30	30" 750	4	6	-	2


(*) 4 for 4" Deep FLEXTRAY
6 for 6" Deep FLEXTRAY

Washer Splice Kits




- 1 Install one kit on each side and remaining kit(s) on bottom.
- 2 Install two kits on each side and remaining kits on bottom.

Splice Plates



Install splice plates on sides and WASHER SPL KIT on bottom.




Splice Bars





Install splice bars on sides and WASHER SPL KIT on bottom.

See page 4 for finish information


Splice Plate Kits for 2" Deep FLEXTRAY

Part Number	System Width		Weight Per 100		Box Quantity	Conveniently poly-bagged for use with 2" Deep FLEXTRAY
	in.	mm	lbs.	kg		
FTS20SK	2"	50	2.91	1.32	10	
	4"	100				
FTS21SK	6"	150	3.63	1.64	10	
	8"	200				
FTS22SK	12"	300	4.35	1.97	10	
	18"	450				
	20"	500				
	24"	600				

Splice Plate Kits for 4" & 6" Deep FLEXTRAY

Part Number	System Width		Weight Per 100		Box Quantity	Conveniently poly-bagged for use with 4" & 6" Deep FLEXTRAY
	in.	mm	lbs.	kg		
FTS23SK	4"	100	5.07	2.30	10	
	6"	150				
	8"	200				
	12"	300				
FTS24SK	18"	450	5.79	2.62	10	
	20"	500				
	24"	600				

See page 4 for finish information



Hanging Supports




Flip Clip™

- Accommodates 1/4" and 3/8" rod sizes
- Installs quickly with a screwdriver or pliers thus reducing installation time
- Requires only one hex nut (not included) to hang and level the FLEXTRAY
- Retainer tabs can be bent over to lock-in the threaded rod and wire basket
- Finishes __: **ZN**, FB, SS6

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
WB46H__	Flip Clip	50	5.2	2.36

Snap retainer stops in place after cable is loaded.




Trapeze Support

- Trapeze Clip installs fast
- For use with trays up to 4" (100mm) deep, 12" (300mm) wide, and spans up to 8'-0" (2.44m)
- Tray can be released from support to allow side cable loading
- Accepts 1/4" and 3/8" threaded rod sizes
- Finishes __: **GS**, BLE

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
TRAPEZE SUPT2__	Trapeze Support Clip	50 trapeze clips 100 retainer stops	7.0	3.17

Snap retainer stops in place after cable is loaded.



See page 4 for finish information


2" Center Hanger

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
2 IN CTR SUPT__	Center Support Hanger for FT2x2	50	5.0	2.27

- For use with 2" (50mm) tray widths only
- Accepts 1/4" threaded rod
- Hardware sold separately
- Finishes __: **GS**, BLE






Assemble with ATTACHMENT CLP & FTHDWE 1/4 hardware.



Hold Down Plate

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
SUPT WASHER__	.28" x .70" 7.1mm x 17.8mm	50	4.7	2.13
FTA6HD__	.40" x .70" 10.1mm x 17.8mm	50	3.5	1.59

- Easy way to mount 4" (100mm) wide tray for raceway run.
- Use 1/4" screws to attach SUPT WASHER to your specific wall/stud application (hardware sold separately).
- FTA6HD can be used in pairs to create a center-hung support using 3/8" rod.
- To protect cables use threaded rod protector (page 21).
- To complete 3/8" center hanger assembly use:
 - 2 - FTA6HD
 - 2 - HN 3/8"-16 hex nuts
- Finish: **ZN**, SS6





See page 4 for finish information

Mounting Bracket

- Designed to support FT2X2X10 Flextray
- Click tabs for FLEXTRAY attachment
- Use 1/4" hardware and washer (not included) to mount bracket
- Finishes __: **SS6**


Part Number	Description	Qty./Box	Wt./Box lbs. kg
FTB2UB__	Light Duty Wall/Rack Bracket	10	2.1 0.95



- Use for light duty cabling applications
- For use with 1 1/2" (38mm) & 2" (51mm) deep tray with 4" (100mm) and 6" (150mm) widths
- When hanging 4" (100mm) wide tray, center hung clip must be run parallel with the tray
- Built-in hold down tab
- Accepts 1/4" threaded rod
- Threaded rod and nuts sold separately
- Finishes __: **GS, BLE**

Center Hung Clip

Part Number	Description	Qty./Box	Wt./Box lbs. kg
CTR HUNG CLP__	Light Duty Center Hanger	50	4.0 1.81




Assemble with 1/4" threaded rod and finned nut



- Use to protect cables from 1/4" to 1/2" threaded rod
- PVC UL94V-O material
- Color: Gray
- Not plenum rated

Threaded Rod Protector

Part Number	Description	Qty./Box	Wt./Box lbs. kg
SB301-1/2x8__	Rod Protector	1	0.03 0.013




See page 4 for finish information


Center Trapeze Hanger

Part Number	Maximum Tray Width		Actual Length		Wt./Pc.	
	in.	mm	in.	mm	lbs.	kg
FTB06CT	6"	150	9.78"	248	0.61	0.27
FTB08CT	8"	200	11.75"	298	0.74	0.33
FTB12CT	12"	300	15.69"	398	0.98	0.44
FTB16CT	16"	400	19.63"	498	1.61	0.73
FTB18CT	18"	450	21.59"	548	1.77	0.80
FTB20CT	20"	500	23.56"	598	1.93	0.87
FTB24CT	24"	600	27.50"	698	2.25	1.02

- Can be installed as center-hung or traditional trapeze hanger
- Multiple options to secure FLEXTRAY to hanger
 - Built in hold down tabs (use screwdriver to bend down tab)
 - Compatible with TOOLLESS CLIP with snap-in locking pin
 - Compatible with WBUHD hold down clip when tray crosswire is aligned over top of hanger
 - Slots and holes for optional hardware attachment
- Corrosion resistant pre-galvanized zinc finish (other finishes available upon request)
- Center hole for up to 1/2" rod
- Hole on each end for up to 3/8" rod
- Threaded rod protector available (SB301-1/2 x 8) see page 21
- When 1/2" trapeze rods are required, add -1/2 to end of part number when ordering



Center Hung



Trapeze

See page 4 for finish information

KwikWire™ Clamps & Wire Rope

- KwikWire system replaces jack chain or ATR to support lighting, ductwork, and FLEXTRAY.
- Can be quickly installed around beams - No drilling required.
- Ideal for sloped ceilings - can hang objects at up to 60° angles.
- Simple height adjustments are made by releasing locking tab, no tools required.
- Spools of wire can be cut to length in field, reducing waste and up front planning.

Part No.	Clamps - For Use With Wire Rope Diameters	Box Qty.
BKC100	1/16" 1.6mm & 3/32" 2.3mm	100
BKC200	1/8" 3.2mm & 3/16" 4.7mm	50



Part No.	Rope Dia.		Working Load		Spool
	in.	mm	Lbs.	kg	
BKW063 ⁽¹⁾	1/16"	1.6	96	43.5	500 ft.
BKW094 ⁽¹⁾	3/32"	2.3	184	83.4	500 ft.
BKW125 ⁽¹⁾	1/8"	3.2	340	154.2	500 ft.
BKW188 ⁽²⁾	3/16"	4.8	840	381.0	250 ft.



Wire Rope Construction



(1) 7 x 7



(2) 7 x 19

KwikWire Clamp Working Loads*

Clamp Part No.	Wire Rope Dia.	Lbs. Safety Factor 5
BKC100	1/16"	0-75
BKC100	3/32"	25-150
BKC200	1/8"	25-250
BKC200	3/16"	50-640

* Working loads shown are for hanging vertically. For suspending at 15°, 30°, 45° or 60° angles from vertical, use the following percentage of the working loads from the chart:

15° = 96%
 30° = 86%
 45° = 70%
 60° = 50%

Cutter Part No.	Box Qty.
BKCC	1



KwikPak™ Wire Rope & Clamps

Part No.	For Use With Wire Rope Diameters	Box Qty.
BKP10063	BKC100 (100 pcs.) 1/16" Ø Wire Rope (500 ft.)	1
BKP10094	BKC100 (100 pcs.) 3/32" Ø Wire Rope (500 ft.)	1
BKP20125	BKC200 (50 pcs.) 1/8" Ø Wire Rope (500 ft.)	1
BKP20188	BKC200 (50 pcs.) 3/16" Ø Wire Rope (250 ft.)	1



See page 4 for finish information

KwikWire™ Accessory Features

- Reduces on the job installation time
- Can be installed quickly without drilling into existing structure
- Increases versatility in the field
- KwikWire accessory system reduces inventory and shipping costs
- No more sawing, filing, or fixing nuts
- Designed for use with cable tray, lighting, and HVAC
- Eliminates the need for all threaded rod
- Cost effective solution for jack chain
- "Y" style accessories require 50% less drilling



KwikWire Accessory Numbering System

Product Line	Assembly Configuration	Leg Termination	Leg Length	Wire Rope Diameter	Straight Length	Assembly or Kit
BK = KwikWire	Blank = Single Leg Y = 2 Legs 3 - 3 Legs	A = Angle Bracket w/Pin H = Hook L = Loop T = Toggle W = Fuse Cut B25 = Bolt w/ 1/4"-20 Thread B38 = Bolt w/ 3/8"-16 Thread BM6 = Bolt w/ M6 Thread BM8 = Bolt w/ M8 Thread BM10 = Bolt w/ M10 Thread	Blank = See Straight Length 18 = 18" Leg 30 = 30" Leg	063 = 1/16" 094 = 3/32"	Blank = Loop w/ Plastic Tube 18 = 18" 30 = 30" 40 = 40" 80 = 80" 120 = 120" 180 = 180" 240 = 240" 360 = 360"	Blank = Assembly Only K = Kit (Assembly & BKC100 Clamp)

Examples

BKYT18-094-120K



KwikWire Accessory

2 legs - toggle leg termination - 18" legs - 1/16" diameter wire - 120" straight length - kit with clamp

BKL-063-120K



KwikWire Accessory

single leg - looped leg termination - 1/16" diameter wire - 120" straight length - kit with clamp

See page 4 for finish information

KwikWire™ 'Y' Style Hook Termination


Part No.	Leg Length		Wire Rope Dia.		Length	
	in.	mm	in.	mm	in.	mm
BKYH18-094-40	18"	457	3/32"	2.3	40"	1016
BKYH18-094-80	18"	457	3/32"	2.3	80"	2032
BKYH18-094-120	18"	457	3/32"	2.3	120"	3048
BKYH18-094-180	18"	457	3/32"	2.3	180"	4572
BKYH18-094-240	18"	457	3/32"	2.3	240"	6096
BKYH18-094-360	18"	457	3/32"	2.3	360"	9144
BKYH30-094-40	30"	762	3/32"	2.3	40"	1016
BKYH30-094-80	30"	762	3/32"	2.3	80"	2032
BKYH30-094-120	30"	762	3/32"	2.3	120"	3048
BKYH30-094-180	30"	762	3/32"	2.3	180"	4572
BKYH30-094-240	30"	762	3/32"	2.3	240"	6096
BKYH30-094-360	30"	762	3/32"	2.3	360"	9144



Box Quantity - 10
5 bags containing 2 pieces per bag

KwikWire™ 'Y' Style Hook Termination With Loop


Part No.	Wire Rope Dia.		Length	
	in.	mm	in.	mm
BKYH18-094	3/32"	2.3	18"	457
BKYH30-094	3/32"	2.3	30"	762



Box Quantity - 10
5 bags containing 2 pieces per bag

- Hook designed to connect up to 3/8" diameter wire.
- Available as a wire rope with hook termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".
- Available in single, double (Y), and triple (3) leg styles

For more information on KwikWire accessories see the KwikWire catalog.




See page 4 for finish information



Shelf Brackets

- Heavy-duty support bracket
- For use with 6" (150mm) to 24" (600mm) wide trays
- Built-in tab for hold down
- Optional hardware (FTSCH) sold separately
- Finishes __: **GLV**, HDG, SS6



Part Number	Use With Tray Width		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTB06CS __	6"	150	1	0.5	0.22
FTB08CS __	8"	200	1	0.6	0.27
FTB12CS __	12"	300	1	1.2	0.54
FTB16CS __	16"	400	1	1.7	0.77
FTB18CS __	18"	450	1	1.9	0.86
FTB20CS __	20"	500	1	2.6	1.18
FTB24CS __	24"	600	1	3.2	1.45




FTB24CS shown

L Brackets

- Installs tray to wall cleanly
- Built-in tab for hold down (not available in stainless steel)
- For use with 4" (100mm) to 24" (600mm) wide trays
- Use with pedestal clamp in raised floor applications
- Optional hardware (FTSCH) sold separately
- Finishes __: **EG**, HD, BLE, 316S

Part Number	Use With Tray Width		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
4 L BRKT __	4"	150	1	0.6	0.27
8 L BRKT __	6" 8"	150 200	1	0.8	0.36
12 L BRKT __	12"	300	1	1.3	0.59
16 L BRKT __	16"	400	1	1.4	0.63
20 L BRKT __	18" 20"	450 500	1	2.0	0.91
24 L BRKT __	24"	600	1	2.3	1.04



Tab can be bent over for hold down.




12 L BRKT


See page 4 for finish information

Z Brackets

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
Z BRKT__	Z Bracket	25	14.0	6.35




- Used for horizontal and/or vertical mounting
- 8" (200mm) wide bracket for use with 4" (100mm) to 32" (800mm) wide trays
- Can be used to offset trays from floor
- Can be used to terminate tray run at wall
- Multiple brackets can be used for wider tray widths
- Finishes __: **GS**, BLE





Use with two (2)
FTSCH
(sold separately)

Hold Down Plate

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
SUPT WASHER__	.28" x .70" 7.1mm x 17.8mm	50	4.7	2.13
FTA6HD__	.40" x .70" 10.1mm x 17.8mm	50	3.5	1.59



- Easy way to mount 4" (100mm) wide tray for raceway run.
- Use 1/4" screws to attach SUPT WASHER to your specific wall/stud application (hardware sold separately).
- FTA6HD can be used in pairs to create a center-hung support using 3/8" rod.
- To protect cables use threaded rod protector (page 21).
- To complete 3/8" center hanger assembly use:
 - 2 - FTA6HD
 - 2 - HN 3/8"-16 hex nuts
- Finish: **ZN**, SS6




See page 4 for finish information

Attachment Clips

- Wall attachment for 2" (50mm) wide tray only (FT2X2X10)
- Low-profile appearance
- Built-in tab to hold down tray
- Can also be used with 2" (50mm) Center Hanger (see page 20)
- Hardware sold separately
- Finishes __: **GS**, BLE


Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
ATTACHMENT CLP__	Support for FT2x2x10	50	3.4	1.54



Mounting Bracket

- Designed to support FT2X2X10 Flextray
- Click tabs for FLEXTRAY attachment
- Use 1/4" hardware and washer (not included) to mount bracket
- Finishes __: **SS6**


Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FTB2UB__	Light Duty Wall/Rack Bracket	10	2.1	0.95



Wall Supports

- Used to attach 2" (50mm) or 4" (100mm) wide trays to walls, struts or cabinets
- Use for raceway mounting
- Mount to metal framing for vertical support
- Tabs are built in for tray hold down
- Mount to side rail for electrical box connection
- Finishes __: **GLV**

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
FTA050CC__	Wall Support Bracket	1	0.8	0.36




See page 4 for finish information

FLEXTRAY™ - Wall Support Methods

Wall Termination Kit

Part Number	Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTA9WTK__	9"	(228)	1	1.3	0.59

- Kit includes all hardware necessary to support FLEXTRAY when terminated at a wall
- Mount slotted angle to wall with up to 3/8" hardware (not included)
- Finishes __: **ZN**, FB, SS6



Wall Termination Kit includes:
1 - Angle with Slots
2 - FTSCH

Wall Mount Kit

Part Number	Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
WB48WMK__	8"	203.2	1	0.76	0.35
WB1224WMK__	12"	304.8	1	1.22	0.55


- Kit includes all components necessary to mount FLEXTRAY to a wall horizontally or vertically
- Mount strut to wall with up to 1/2" hardware (not included)
- Finish: Channel - **GLV**
Hardware - **ZN**
Available in SS6




WB1224WMK shown

Wall Mount Kit includes:

WB48WMK	WB1224WMK	
1	1	B54SH Strut
1	2	SUPT WASHER Hold Downs
1	2	1/4"-20 x 1" Slotted Head Screw
1	2	N224WO Channel Nut



Vertically Mounted




Horizontally Mounted



C Brackets

- Tab can be used for hold down (stainless steel will not have these tabs)
- For use with 4" (100mm) to 12" (300mm) wide trays
- C Bracket attaches to hard ceiling types
- All brackets are 7⁷/₈" (200mm) tall
- Cables can be side loaded
- L Brackets (page 27) and C Brackets can be combined for layered tray runs
- Finishes __: **EG**, BLE, HD

Part Number	Tray Width - Up To		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
4 C BRKT__	4"	100	1	1.2	0.54
8 C BRKT__	8"	200	1	1.4	0.63
12 C BRKT__	12"	300	1	1.9	0.86



Assemble with
SUPT WASHER &
FTHDWE 1/4.



See page 4 for finish information

FLEXTRAY™ - F.A.S.T.™ Underfloor System

The F.A.S.T. System is an innovative and flexible way to support and manage cables in raised floor applications. This Foldable, Adjustable, Stackable, Tool-less System uses FLEXTRAY, stands, and accessories to provide a variety of options for your project and the fastest installation time on the market. Best of all, it does not attach to the raised floor structure and can be installed either before or after floor is in place.




FAST System



F.A.S.T. System Flextray

- Rounded ends on all wires
- UL Classified (see technical data for details)
- Depths: 2" (50mm), 4" (100mm), & 6" (150mm) nominal
- Lengths: 24" (609mm), 48" (1219mm), & 118" (2997mm)
- Use flat fitting (WBUFLT) for turns
- Wire Diameter: 0.191" (4.9mm)
- Standard finishes: **GLV**


Consult customer service for other available finishes




	Part Number	Width		Length		LD		H		Wt. Per Pc.	
		in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kg
2" (50mm) deep	FTU2X6X2	6"	150	23.9"	603	2.38"	60	2.77"	70	2.03	0.92
	FTU2X6X4	6"	150	47.5"	1206	2.38"	60	2.77"	70	3.95	1.79
	FTU2X6X10	6"	150	118.4"	3008	2.38"	60	2.77"	70	9.72	4.41
	FTU2X12X2	12"	300	23.9"	603	2.38"	60	2.77"	70	2.99	1.36
	FTU2X12X4	12"	300	47.5"	1206	2.38"	60	2.77"	70	5.82	2.64
	FTU2X12X10	12"	300	118.4"	3008	2.38"	60	2.77"	70	14.32	6.50
	FTU2X20X2	20"	500	23.9"	603	2.38"	60	2.77"	70	4.28	1.94
	FTU2X20X4	20"	500	47.5"	1206	2.38"	60	2.77"	70	8.33	3.78
	FTU2X20X10	20"	500	118.4"	3008	2.38"	60	2.77"	70	20.45	9.28
4" (100mm) deep	FTU4X6X2	6"	150	23.9"	603	4.38"	111	4.77"	121	2.67	1.21
	FTU4X6X4	6"	150	47.5"	1206	4.38"	111	4.77"	121	5.20	2.36
	FTU4X6X10	6"	150	118.4"	3008	4.38"	111	4.77"	121	12.79	5.80
	FTU4X12X2	12"	300	23.9"	603	4.38"	111	4.77"	121	3.64	1.65
	FTU4X12X4	12"	300	47.5"	1206	4.38"	111	4.77"	121	7.08	3.21
	FTU4X12X10	12"	300	118.4"	3008	4.38"	111	4.77"	121	17.39	7.89
	FTU4X20X2	20"	500	23.9"	603	4.38"	111	4.77"	121	4.93	2.24
	FTU4X20X4	20"	500	47.5"	1206	4.38"	111	4.77"	121	9.58	4.35
	FTU4X20X10	20"	500	118.4"	3008	4.38"	111	4.77"	121	23.52	10.67
6" (150mm) deep	FTU6X6X2	6"	150	23.9"	603	6.38"	162	6.77"	172	3.32	1.51
	FTU6X6X4	6"	150	47.5"	1206	6.38"	162	6.77"	172	6.45	2.93
	FTU6X6X10	6"	150	118.4"	3008	6.38"	162	6.77"	172	15.85	7.19
	FTU6X12X2	12"	300	23.9"	603	6.38"	162	6.77"	172	4.28	1.94
	FTU6X12X4	12"	300	47.5"	1206	6.38"	162	6.77"	172	8.33	3.78
	FTU6X12X10	12"	300	118.4"	3008	6.38"	162	6.77"	172	20.45	9.28
	FTU6X20X2	20"	500	23.9"	603	6.38"	162	6.77"	172	5.57	2.53
	FTU6X20X4	20"	500	47.5"	1206	6.38"	162	6.77"	172	10.83	4.91
	FTU6X20X10	20"	500	118.4"	3008	6.38"	162	6.77"	172	26.59	12.06
Flats	WBUFLT	20"	500	24"	604	-	-	-	-	2.96	1.34
	WBUFLT-12	12"	250	24"	604	-	-	-	-	1.50	0.68
	WBUFLT-06	6"	150	24"	604	-	-	-	-	1.00	0.45

See page 4 for finish information


Stands



- No tools required for installation
- Formed top surface free of protrusions or sharp edges
- Up to 6" height adjustment
- Inside and outside leg positioning
- Folded and boxed for ease in shipping
- Patent Pending
- Stand part number includes:
 - one (1) stand
 - two (2) feet
 - two (2) adhesive pads
 - two (2) hold down clips
- Standard finish: Pre-Galvanized



WBU2016 stands shown in double tier application. Feet and adhesive pads not required for second tier assembly.



Part Number	Max. Basket Width		Height Adjustment		Stands Per Box	Wt. Per Box	
	in.	mm	in.	mm		lbs.	kg
FTU120404	12"	300	4"	101	2	1.82	0.82
FTU120608	12"	300	6"-8"	152-203	2	2.79	1.26
WBU1216	12"	300	10"-16"	254-406	2	7.44	3.37
WBU1224 *	12"	300	18"-24"	457-609	2	9.06	4.11
WBU1231 *	12"	300	25"-31"	635-787	2	10.52	4.77
FTU200404	20"	500	4"	101	2	2.34	1.06
FTU200608	20"	500	6"-8"	152-203	2	3.36	1.52
WBU2016	20"	500	10"-16"	254-406	2	8.56	3.88
WBU2024	20"	500	18"-24"	457-609	2	10.20	4.62
WBU2031 *	20"	500	25"-31"	635-787	2	11.64	5.28

* Legs are packed separately in box and not inserted in stand.

See page 4 for finish information

Cantilever Kits & Accessories



- No tools required for installation
- Simple design for tiered applications
- Available in kits or individual parts
- Adjustable shelf height
- Formed top surface has no sharp edges
- Can be installed independent of raised floor
- Standard finish: Pre-Galvanized



Adjustability of shelf brackets

WBUCK812 Double Tier Cantilever Kit Shown with WBU2016 Stand



1



2

WBUCK12 - Single Tier Cantilever Kit Includes

- (1) WBUKB12
- (1) WBUL16
- (1) WBUKF
- (2) WBUHD

WBUCK812 - Double Tier Cantilever Kit Includes

- (1) WBUKB8
- (1) WBUKB12
- (1) WBUL24
- (1) WBUKF
- (3) WBUHD





3

WBUKB8



4

WBUKB12



Part Number	Item #	Description	Max Height †		Box Qty.	Wt. Per Box	
			in.	mm		lbs.	kg
WBUCK12 *	1 ^Δ	Cantilever Kit - Single Tier with 12" Bracket	7.30"	185	10	15.62	7.08
WBUCK812	2 ^Δ	Cantilever Kit - Double Tier with 8" & 12" Brackets	15.25"	387	10	25.40	11.52
WBUKB8	3	8" Cantilever Bracket for 6" Flextray	-	-	10	5.51	2.50
WBUKB12	4	12" Cantilever Bracket for up to 12" Flextray	-	-	10	9.16	4.15
WBUL16	5	Short Vertical Support	7.30"	185	10	4.37	1.98
WBUL24	6	Medium Vertical Support	15.25"	387	10	8.45	3.83
WBUL31	7	Tall Vertical Support	22.25"	565	10	12.07	5.47

* For use with 2" and 4" deep Flextray on the lower level.

† Height - from top of stand

Δ Stand not included

See page 4 for finish information

FLEXTRAY™ - F.A.S.T.™ Underfloor System

Hold Down Clip



- Spring steel clip to attach Flextray to stands
- No tools required for installation
- Holds both continuous and spliced wire sections securely
- Works with stands and cantilever brackets



Part Number	Item #	Description	Box Qty.	Wt. Per Box	
				lbs.	kg
WBUHD	8	Basket Clip	50	1.10	0.50

Pedestal Clip



- Optional spring steel clip to give added rigidity to system
- Works with stands and cantilever brackets




Part Number	Item #	Description	Box Qty.	Wt. Per Box	
				lbs.	kg
WBUPC	9	Pedestal Clip	50	1.65	0.75

Cantilever Foot




Part Number	Item #	Description	Box Qty.	Wt. Per Box	
				lbs.	kg
WBUCF	10	Cantilever Foot	50	8.65	3.92

Under Floor Stand



- Heights of 3", 4", 5" or 6"
- Leg cutout allows for airflow
- No tools required to mount FLEXTRAY to stand
- Use WBUHD hold down clips to secure basket
- Stand width is 12"
- Fasten to floor for maximum stability
- Floor mounting slot size: .313" (7.9mm) x .813" (20.6mm) for 1/4" hardware



Part Number	Overall Height		Wt. Per Each	
	in.	mm	lbs.	kg
WBU1203	3"	76	1.32	0.60
WBU1204	4"	101	1.60	0.72
WBU1205	5"	127	1.88	0.85
WBU1206	6"	152	2.17	0.98

See page 4 for finish information

L Bracket & Toolless Clip

- For use when access to ground floor is limited
- Use with round post sizes 0.9" (25mm) through 1.2" (30mm)
- Use with square posts
- Order clamps and brackets separately
- Built-in tab for hold down
- Tool-less Clip (plenum-rated material) - Snap-in locking pin securely holds basket to bracket



Illustration photos.
All parts are sold separately.

Part Number	Description	Qty.	Wt. Per Box	
			lbs.	kg
TOOLESS CLIP	Tool-less Hold-Down Clip	50/Box	1.00	0.45

Brackets (Zinc Plated)


Part Number	System Width		Length		Box Qty.	Wt. Per Box	
	in.	mm	in.	mm		lbs.	kg
8 L BRKT	6"-8"	150-200	8"	200	1	0.80	0.36
12 L BRKT	12"	300	12"	300	1	1.30	0.59

Pedestal Clamp & Kit


- Clamps to existing raised-access floor stanchion
- Use L BRKT (shown above) or full pedestal kit to support trays under the raised access floor (sold separately)
- For tray widths 2" (50mm) to 20" (500mm)
- *Pedestal Clamp Kit includes two (2) pedestal clamps, 28" (711mm) profile section, bolts & nuts
- Kits include hardware
- SUPTWASHER & FTTHDWE 1/4 sold separately
- Finishes __: **EG**



Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
PEDESTAL CLAMP__	Pedestal Clamp	1	0.6	0.27
PEDESTAL KIT__	Pedestal Clamp Kit	1*	3.3	1.49



Pedestal kits are recommended for tray widths of 16" (400mm) or greater




See page 4 for finish information

Under Floor Support Bracket



- Under Floor Support Bracket provides rugged support for FLEXTRAY System from access floor post.
- To complete the installation, the following hardware must be ordered separately.
 - (2) - B501 U-Bolts
 - (1) - SUPT WASHER Hold Down
 - (1) - 1/4"-20 x 1" Slotted Head Screw
 - (1) - N224WO Channel Nut
- Finish: **ZN**




Part Number	'A'		Box Quantity	Wt. Per Box	
	in.	mm		lbs.	kg
B409UF-12	12"	300	1	3.6	1.63
B409UF-18	18"	450	1	4.5	2.04
B409UF-21	21"	533	1	5.4	2.45


U-Bolts



- Designed for attachment of Under Floor Support Brackets to access floor post. Each U-Bolt includes two (2) hex nuts.
- Finish: **ZN**




Part Number	'A'		Thread Size	Box Quantity	Wt. Per Box	
	in.	mm			lbs.	kg
B501-1	1 ³ / ₈ "	30	5/16"-18	50	7.0	3.17
B501-1¹/₂	2"	50	5/16"-18	50	8.0	3.63
B501-2	2 ⁷ / ₁₆ "	62	3/8"-16	20	5.4	2.45
B501-2¹/₂	2 ¹⁵ / ₁₆ "	75	3/8"-16	25	8.0	3.63



See page 4 for finish information


Ground Bolt

- Attaches up to #1 ground wire to each tray section when separate ground wire is required
- Used for UL grounding compliance.
- When using color powder coated finish or paint, coating must be removed at the points of contact.
- Finish: Copper Plated



Part Number	Description	Qty./Box	Wt./Box lbs. kg	
GROUND BOLT	Ground Bolt	1	0.11	0.05

Adhesive & Feet




- WBUTAPE - Double-sided adhesive pads for temporary positioning of floor stands
Pad Size: 2" (50mm) x 4" (100mm)
- WBUFA - Adhesive to secure stand to floor

Part Number	Description	Box Quantity	Wt. Per Box lbs. kg	
WBUF	Stand Foot	10	2.36	1.07
WBUTAPE	Double-Sided Tape	50	2.50	1.13
WBUFA	Floor Adhesive	1 Gallon	10.78	4.89

Floor Stand

- Non-metallic snap lock floor stand is designed for use under access floors.
- Floor stand elevates FLEXTRAY System 1⁵/₈" (41.3mm) above the floor.
- To attach floor stand, use construction adhesive or anchors.
- Elevation increments of 1³/₈" (35mm) can be obtained by stacking floor stands.
- Sized for 1/4" hardware (order separately).
- Material: Black Plenum-rated Plastic




Part Number	Wt. Per Pc. lbs. kg		Box Quantity
FTA2FS	0.44"	0.20	10

See page 4 for finish information



Covers

- Protects cable from debris and dust
- Adds security to cable installation
- Easy bend-over tabs secure cover to trays
- Available for 2" (50mm) to 24" (600mm) wide trays
- Comes in 118" (2997mm) length
- Finishes __: **GS**, BLE, 304S, 316S




Part Number	For Tray Width Of		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
2 IN COVER __	2"	50	1	3.8	1.72
4 IN COVER __	4"	100	1	5.7	2.58
6 IN COVER __	6"	150	1	6.7	3.04
8 IN COVER __	8"	200	1	8.7	3.94
12 IN COVER __	12"	300	1	11.6	5.26
16 IN COVER __	16"	400	1	15.6	7.07
18 IN COVER __	18"	450	1	17.0	7.71
20 IN COVER __	20"	500	1	18.5	8.39
24 IN COVER __	24"	600	1	22.0	9.98





Dividers

- Allows cable separation within a single tray
- Hemmed/rounded edge provides cable jacket safety
- Hardware included
- Field miter for bends and turns
- Dual slots every 24" (609mm) for field cutting
- Available in 2" (50mm), 4" (100mm) and 6" (150mm) heights
- Comes in 118.125" (3000mm) length
- Finishes __: **GS**, BLE, 304S, 316S

Part Number	For Tray Depth Of		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
2 IN DIVIDER __	2"	50	1	3.5	1.59
4 IN DIVIDER __	4"	100	1	9.6	4.35
6 IN DIVIDER __	6"	150	1	14.5	6.58



Dividers include hardware shown below



See page 4 for finish information


Solid Bottom Inserts

Part Number	For Tray Width Of		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
INSERT 4X118__	4"	100	1	6.8	3.08
INSERT 6X118__	6"	150	1	9.8	4.44
INSERT 8X118__	8"	200	1	13.3	6.03
INSERT 12X118__	12"	300	1	21.6	9.80
INSERT 16X118__	16"	400	1	26.4	11.97
INSERT 18X118__	18"	450	1	32.4	14.69
INSERT 20X118__	20"	500	1	32.9	14.92
INSERT 24X118__	24"	600	1	39.3	17.82

- Continuous support for sensitive cables
- Security of cable in high-traffic areas
- Hardware included
- Available for 4" (100mm) to 24" (600mm) wide trays
- Comes in 118" (2997mm) length
- Finishes __: **GS**, BLE, 304S, 316S



Attachment methods



Attach with
FTHDWE 1/4
& Top Washer





Blind Ends

Part Number	'A'		Height		Box Quantity
	in.	mm	in.	mm	
FT BE 2X2	2"	50	2"	50	1
FT BE (*)X4	4"	100	(*)	(*)	1
FT BE (*)X6	6"	150	(*)	(*)	1
FT BE (**X)8	8"	200	(*)	(*)	1
FT BE (**X)12	12"	300	(**)	(**)	1
FT BE (**X)16	16"	400	(**)	(**)	1
FT BE (**X)18	18"	450	(**)	(**)	1
FT BE (**X)20	20"	500	(**)	(**)	1
FT BE (**X)24	24"	600	(**)	(**)	1

- Forms a closure for a dead-end FLEXTRAY
- Hardware included
- Finish: **GLV**, SS6

(*) Insert: 2 = 2" (50 mm), 4 = 4" (100 mm) for height

(**) Insert: 2 = 2" (50 mm), 4 = 4" (100 mm),
6 = 6" (150 mm) for height




See page 4 for finish information

Cable Roller

- Protects and maintains recommended cable radii for Cat 5, Cat 5E, Cat 6, Cat 6A, Fiber, etc.
- Height of roller can be adjusted to tray depth
- Installs in seconds with no tools
- Reduces cable installation time
- Prevents migration of cables
- For use with 4" (100mm) to 32" (800mm) tray widths
- Finish: Cast Aluminum

Part Number	Description	Qty./Box	Wt./Box lbs. kg
CABLE ROLLER	Cable Roller	1	1.0 0.45



Quick, snap-together design

- Securely holds tray to support
- Snap-in locking pin
- No tools or fastening required
- Fastest hold-down method available
- For use with the following:
 - FTB_CS (see pg. FLX-27)
 - L BRKT (see pg. FLX-27)
 - C BRKT (see pg. FLX-31)
- Finish: Plenum rated resin (black)

Toolless Clip


Part Number	Description	Qty./Box	Wt./Box lbs. kg
TOOLLESS CLIP	Toolless Hold-Down Clip	50	1.0 0.45



- Use to secure FLEXTRAY to horizontal strut support
- Designed for use as shown in drawing (no load rating)
- Finish: Black Zinc Phosphate

Strut Mounting Clip

Part Number	Description	Qty./Box	Wt./Box lbs. kg
BW4	Strut Mounting Clip	100	0.9 0.41




See page 4 for finish information

Drop Out Fitting

Part Number	Description	Qty./Box	Wt./Box lbs. kg
DROP OUT__	Drop Out Fitting	50	15.0 6.8


- Keeps cable radius secure at drop point
- For use with 4" (100mm) to 32" (800mm) wide trays
- Attaches to tray without hardware
- Drop outs can be attached at bottom, side or ends of tray
- Hold down tabs on bottom of drop out to secure tray
- Finishes __: **EG**, BLE, SS6



Cable Drop Out

Part Number	Description	Qty./Box	Wt./Box lbs. kg
FTA2DO	Cable Drop Out	10	0.17 0.08


- Non-metallic 2" (50mm) radius Cable Drop-Out snap locks into mesh bottom and protects cables from sharp bend
- Material: Black Plenum-rated Plastic



See page 4 for finish information

Conduit Connector

- Conduit connector is designed to connect conduit to the side or bottom of FLEXTRAY
- Conduit bushing will remain outside of tray to keep cable pathway clear
- Bend tabs to secure connector to tray
- No hardware included
- Finishes __: **GLV**




Part Number	Conduit Size		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTA050CC__	1/2"	15	10	2.0	0.91
FTA075CC__	3/4"	20	10	2.0	0.91
FTA100CC__	1"	25	10	2.0	0.91
FTA125CC__	1 1/4"	32	10	2.0	0.91



Rack Clamp

- Securely holds tray down to rack
- Installs without drilling
- Black-painted finish to match rack
- Finish__: **BLE**




Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
RACK CLAMP__	Rack Clamp	4	4.7	2.13



Adaptor Kit

- Adaptor kit includes all hardware necessary to connect Flextray system to top of relay rack at right angle or parallel position
- Finish__: **YZN (Yellow Zinc Chromate)**



Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
SB2204__	Adaptor Kit	1	0.37	0.17

Adaptor Kit includes:

- (1) - Mounting Plate
- (2) - 5/16"-18 x 2" "J"-Bolts
- (2) - HN 5/16"-18 Hex Nuts
- (2) - LW 5/16" Lock Washers





See page 4 for finish information

Radius Shield

Part Number	Height A		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
FTA2RS	2.5	63	50	4.0	1.8
FTA4RS	4.3	110	50	7.0	3.2
FTA6RS	5.9	150	25	5.0	2.3


- Provides a smooth inside radius surface.
- No tools or fasteners needed to install.
- Sizes for 2", 4" & 6" deep FLEXTRAY; 90° horizontal bends, tees, and crosses.
- Installs in seconds. Simply hold in place and bend back tabs.
- Slick surface to reduce cable friction.
- Material: Black Polycarbonate



Rubber Cap

Part Number	Box Quantity	Wt. Per 100	
		lbs.	kg
B719EB	100	0.20	0.10

- Install on wire ends if required. Fits all wire diameters




Part Number	Color	Qty./Box	Wt./Box	
			lbs.	kg
SB420ATG	Gray Lacquer	1	0.9	0.41
SB420AFB	Flat Black Lacquer	1	0.9	0.41
SB420ACW	Computer White Lacquer	1	0.9	0.41
B999	Silver Zinc-Rich Paint	1	0.9	0.41

- Size: 12 ounce aerosol can
- Cannot ship air freight

See page 4 for finish information

Label Clip

- Clips easily into trays
- Use for identifying your cable pathways
- Can be used on all tray sizes
- Will not fit on side of 1 1/2" deep FLEXTRAY
- Finish: Non-plenum-rated resins




Part Number	Length		Qty./Box	Wt./Box	
	in.	mm		lbs.	kg
LABEL CLIP	10 1/2"	267	10	0.6	0.27



Ground Bolt

- Attaches up to #1 ground wire to each tray section when separate ground wire is required
- Used for UL grounding compliance.
- When using color powder coated finish or paint, coating must be removed at the points of contact.
- Finish: Copper Plated




Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
GROUND BOLT	Ground Bolt	100	1.0	0.45



Ground Wire Supports

- Supports ground wire along side of tray
- Can be used on all trays
- Finish __: Zinc Plated



Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
GROUND SUPT GL	Ground Wire Support	100	0.6	0.27



See page 4 for finish information

- Complete source of hardware for ceiling connections
- Available in stock
- Strut can be purchased in pre-cut lengths and various colors
- All hardware is zinc plated

Threaded Rod



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
ATR1/4x72	1/4" x 72" (1828mm)	1	0.7	0.31
ATR1/4x120	1/4" x 120" (3048mm)	1	1.2	0.54
ATR1/4x144	1/4" x 144" (3657mm)	1	1.4	0.63
ATR3/8x72	3/8" x 72" (1828mm)	1	1.7	0.77
ATR3/8x120	3/8" x 120" (3048mm)	1	2.9	1.31
ATR3/8x144	3/8" x 144" (3657mm)	1	3.5	1.58
ATR1/2x72	1/2" x 72" (1828mm)	1	3.2	1.45
ATR1/2x120	1/2" x 120" (3048mm)	1	5.4	2.45
ATR1/2x144	1/2" x 144" (3657mm)	1	6.5	2.95

Rod Couplings



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
B655-1/4	1/4"-20	50	2.0	0.91
B655-3/8	3/8"-16	50	5.5	2.49
B655-1/2	1/2"-13	50	6.0	2.72

Hex Nuts



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
1/4HN	1/4"-20	100	0.6	0.27
3/8HN	3/8"-16	100	1.6	0.72
1/2HN	1/2"-13	100	4.3	1.95

Lock Washers



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
1/4LW	1/4"	200	0.6	0.27
3/8LW	3/8"	200	1.6	0.72
1/2LW	1/2"	200	2.0	0.91

Flat Washers



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
1/4FW	1/4"	200	1.2	0.54
3/8FW	3/8"	200	3.0	1.36
1/2FW	1/2"	200	6.6	2.99

Square Washers



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
B201	7/16	50	6.0	2.72
B202	9/16	50	7.0	3.17

Beam Clamps



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
B3036L-3/8	3/8"-16	100	60.0	27.2
B3036L-1/2	1/2"-13	100	140.0	63.5

See page 4 for finish information

Beam Clamps



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
B444-1/4	1/4"-20	100	160	72.5
B444-3/8	3/8"-16	100	430	195.0
B444-1/2	1/2"-13	100	430	195.0

U-Bolt Clamps



Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
B441-22	3/8"-16 x 3 3/8" long	100	160	72.5

Spring Nuts



Part Number	Thread Size	Qty.	Wt./Qty.	
			lbs.	kg
N224	1/4"-20	100	6.5	2.95
N228	3/8"-16	100	9.3	4.22
N225	1/2"-13	100	11.3	5.12

Bolted Framing

B22S B22SH B56SH B56S



Part Number	Channel Size	Qty.	Wt./Qty.	
			lbs.	kg
B22SGALV120	1 5/8" x 120" - 12 ga.	1	6.0	2.72
B22SHGALV120	1 5/8" x 120" - 12 ga.	1	6.0	2.72
B56SGALV120	1 3/16" x 120" - 15 ga.	1	7.0	3.17
B56SHGALV120	1 3/16" x 120" - 15 ga.	1	6.0	2.72

Concrete Rapid Rod Hanger



Part Number	Rod Size	Shank Size	Qty.	Wt./Qty.	
				lbs.	kg
ARC-37-150	3/8"	1/4" x 1 1/2"	100	3.4	1.54

Wood Rapid Rod Hanger



Part Number	Rod Size	Shank Size	Qty.	Wt./Qty.	
				lbs.	kg
ARW-37-200	3/8"	1/4" x 2"	100	3.4	1.54
ARW-37-200SW	3/8"	1/4" x 2"	100	3.4	1.54

SW = Side Mount

Steel Rapid Rod Hanger




Part Number	Rod Size	Shank Size	Qty.	Wt./Qty.	
				lbs.	kg
ARS-37-150	3/8"	1/4" x 1 1/2"	100	3.4	1.54
ARS-37-150SW	3/8"	1/4" x 1"	100	3.4	1.54

SW = Side Mount

Sockets for Rapid Rod Hangers

Part Number	Size	Qty.	Wt./Qty.	
			lbs.	kg
7187	Universal Steel & Wood Socket	1	4.5	2.04
7197	3/8" Concrete Socket	1	4.5	2.04

See page 4 for finish information



Flextray Cutters

- Exclusive, patented CLEANSHEAR™ cuts tray fast
- No sharp edges
- Designed specifically for cutting Flextray
- Safely cut and bend Flextray into any configuration

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
CLEANSHEAR	CLEANSHEAR Cutting Tool	1	4.3	1.95



Patented



1 Face tray up. Slide cutter next to vertical wire and cut.



2 Turn tray to the side with open side facing you. Repeat step 1 to cut wire.



3 Finish cutting all side wires.



4 Turn tray open-side down and cut wires from bottom of tray.



5 Finish cutting by moving to other side of tray to cut remaining wires,


- CLEANSHEAR Bender has our exclusive bending attachment
- Makes bending larger trays easy
- Recommended for bending tray widths of 16" (400mm) or greater

Flextray Bender

Part Number	Description	Qty./Box	Wt./Box	
			lbs.	kg
CLEANSHEAR BEND	CLEANSHEAR Cutting Tool With Bender Attachment	1	5.4	2.45




Patented




Angular Bolt Cutter

Part Number	Description	Qty./Box	Wt./Box lbs. kg	
WB30BC	Bolt Cutter	1	6.8	3.1
WB30RB	Replacement Blade	1	1.3	0.6





WB30BC
Angular Bolt Cutter



WB30RB
Replacement Blade

Completely adaptable, our Flextray is designed to accommodate jobsite changes. Cut wires with our Angular Bolt Cutter, bend to create a bend, tee, or reducer.

Cut and remove each wire as illustrated below. Follow cutting pattern and blade positioning. Placing Flextray open side down provides the optimum cutting angle.



Cutting Order

For the best results, use a WB30BC Angular Blade Offset Bolt Cutter with 24" (600 mm) long handles. The Offset Blade Cutter produces a clean cut. Position bolt cutter blades near the cross wire and perpendicular to wire to be cut (see illustration above). Proper cut will make the assembly faster, easier and safer while minimizing grinding.

Part Number	Length		Wt. Per Cutter		Box Quantity
	in.	mm	lbs.	kg	
WB50WC	12 ³ / ₄ "	325	3.0	1.3	1

Part Number	Description	Box Quantity
WB50RB	Replacement Blade	1
WB50BA	Replacement Battery	1

The Greenlee cable wire cutter makes flush cuts without burrs. Will cut .191" (4.8mm) diameter wire in 2 seconds. Cutting head rotates 330° for ease of positioning and the tool automatically retracts when cut is complete.


Comes with 2 batteries, charger, and carrying case. Approximately 250 cuts per charge.



See page 4 for finish information


90° Horizontal Bends (Short Radius)

- Make your own field cut horizontal bends using CLEANSHEAR™ to make safe, smooth cuts
- Can be made from any tray width and depth with any available finish
- SUPT WASHER & FTHDWE 1/4 hardware may be used on bottom of tray instead of WASHER SPL KIT where desired




2" (50mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
2"	50	WASHER SPL KIT	1




4" (100mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
1 1/2"	38	WASHER SPL KIT	1
2"	50	WASHER SPL KIT	1
4"	100	WASHER SPL KIT	1




6" (150mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
1 1/2"	38	WASHER SPL KIT	1
2"	50	WASHER SPL KIT	1
4"	100	WASHER SPL KIT	1



8" (200mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
1 1/2"	38	WASHER SPL KIT	1
2"	50	WASHER SPL KIT	1
4"	100	WASHER SPL KIT	1
6"	150	WASHER SPL KIT	1



12" (300mm) Tray Width


Flextray Depth		Required Hardware Description	Quantity
in.	mm		
1 1/2"	38	WASHER SPL KIT	1
2"	50	WASHER SPL KIT	1
4"	100	WASHER SPL KIT	1
6"	150	WASHER SPL KIT	1

90° Horizontal Bends (Short Radius)

- Make your own field cut horizontal bends using CLEANSHEAR™ to make safe, smooth cuts
- Can be made from any tray width and depth with any available finish
- SUPT WASHER & FTHDWE 1/4 hardware may be used on bottom of tray instead of WASHER SPL KIT where desired


16" (400mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
2"	50	WASHER SPL KIT	3
4"	100	WASHER SPL KIT	3
6"	150	WASHER SPL KIT	3




18" (450mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
2"	50	WASHER SPL KIT	3
4"	100	WASHER SPL KIT	3
6"	150	WASHER SPL KIT	3




20" (500mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
2"	50	WASHER SPL KIT	3
4"	100	WASHER SPL KIT	3
6"	150	WASHER SPL KIT	3




24" (600mm) Tray Width

Flextray Depth		Required Hardware Description	Quantity
in.	mm		
2"	50	WASHER SPL KIT	3
4"	100	WASHER SPL KIT	3
6"	150	WASHER SPL KIT	3



90° Horizontal Bends (Long Radius)


- Make your own field cut horizontal sweeps using CLEANSHEAR™ to make safe, smooth cuts
 - Can be made from any tray width and depth with any available finish
 - Cut as many segments as required to control sweep radius (use chart for recommendations)
 - One (1) WASHER SPL KIT is required to connect each cut segment minus one, this segment uses one (1) SPLICE BAR, two (2) FTHDWE 1/4 and two (2) BTM WASHER
- Illustration shown below is for a 8" (200mm) width
 - 1.5" deep FLEXTRAY has only one (1) side wire
 - 2" deep FLEXTRAY has two (2) side wires - shown
 - 4" deep FLEXTRAY has three (3) side wires
 - 6" deep FLEXTRAY has four (4) side wires



Flextray Width in. mm	Segments To Be Removed	Component Qty.		
		WASHER SPL KIT	FTHDWE 1/4 & BTM WASHER	SPLICE BAR
4" 100	2	1	2	1
6" 150	3	2	2	1
8" 200	4	3	2	1
12" 300	6	5	2	1
16" 400	7	6	2	1
18" 450	8	7	2	1
20" 500	10	9	2	1
24" 600	11	10	2	1
30" 750	13	12	2	1
32" 800	13	12	2	1

90° Horizontal Bend From (2) Straight Sections



- Cut required number of wire side sections listed in chart per the illustration below (Illustration is for a 8" (200mm) width)
- 1.5" deep FLEXTRAY has only one (1) side wire
- 2" deep FLEXTRAY has two (2) side wires - shown
- 4" deep FLEXTRAY has three (3) side wires
- 6" deep FLEXTRAY has four (4) side wires



Flextray Width in. mm	Side Sections To Be Removed	WASHER SPL KIT Qty.
4" 100	1	2
6" 150	2	2
8" 200	2	2
12" 300	3	2
16" 400	4	3
18" 450	5	3
20" 500	5	3
24" 600	6	4
30" 750	8	4
32" 800	8	4

Reducers


Large Flextray Width		WASHER SPL KIT		Component Qty. FTHDWE 1/4 & BTM WASHER		SPLICE BAR	
in.	mm	(SR)	(LRR)	(SR)	(LRR)	(SR)	(LRR)
4"	100	-	1	-	2	-	1
6"	150	-	2	-	2	-	1
8"	200	1	2	4	2	2	1
12"	300	2	3	4	2	2	1
16"	400	2	3	4	2	2	1
18"	450	2	3	4	2	2	1
20"	500	3	3	4	2	2	1
24"	600	3	3	4	2	2	1
30"	750	3	3	4	2	2	1
32"	800	3	3	4	2	2	1



- 1.5" deep FLEXTRAY has only one (1) side wire
- 2" deep FLEXTRAY has two (2) side wires - shown
- 4" deep FLEXTRAY has three (3) side wires
- 6" deep FLEXTRAY has four (4) side wires


Vertical Inside & Outside Bends

- Cut wire section as shown and bend to desired angle
- 1.5" deep FLEXTRAY has only one (1) side wire
- 2" deep FLEXTRAY has two (2) side wires - shown
- 4" deep FLEXTRAY has three (3) side wires
- 6" deep FLEXTRAY has four (4) side wires



Horizontal Tees (and crosses)

- Cut wire side sections as shown in the illustration below (Illustration is for a 8" (200mm) width)
- 1.5" deep FLEXTRAY has only one (1) side wire
- 2" deep FLEXTRAY has two (2) side wires - shown
- 4" deep FLEXTRAY has three (3) side wires
- 6" deep FLEXTRAY has four (4) side wires
- For crosses, duplicate process on opposite side



Tray Width in.	mm	WASHER SPL KIT Qty.
2"	50	2
4"	100	2
6"	150	3
8"	200	3
12"	300	4
16"	400	4
18"	450	4
20"	500	4
24"	600	4
30"	750	5
32"	800	5

Catalog No.	Page	Catalog No.	Page	Catalog No.	Page
Straight Sections		Accessories		Accessories	
FT1.5X4X10	6	1/4 FW	48	B441-22	49
FT1.5X6X10	6	1/4 HN	48	B444-1/4	49
FT1.5X8X10	6	1/4 LW	48	B444-3/8	49
FT1.5X10X10	6	3/8 FW	48	B444-1/2	49
FT2X2X10	6	3/8 HN	48	B501-1	38
FT2X4X10	6	3/8 LW	48	B501-11/2	38
FT2X6X10	6	1/2 FW	48	B501-2	38
FT2X8X10	6	1/2 HN	48	B501-21/2	38
FT2X12X10	6	1/2 LW	48	B655-1/4	48
FT2X16X10	6	2 IN DIVIDER	41	B655-3/8	48
FT2X18X10	6	2 IN CTR SUPT	20	B655-1/2	48
FT2X20X10	6	4 C BRKT	31	B719EB	46
FT2X24X10	6	4 IN DIVIDER	41	B999	46
FT2X30X10	6	4 L BRKT	27	B3036L-3/8	48
FT2X22X10	6	6 IN DIVIDER	41	B3036L-1/2	48
FT4X4X10	7	8 C BRKT	31	BKC100	23
FT4X6X10	7	8 L BRKT	27, 37	BKC200	23
FT4X8X10	7	12 C BRKT	31	BKCC	23
FT4X12X10	7	12 L BRKT	27, 37	BKP10063	23
FT4X16X10	7	16 L BRKT	27	BKP10094	23
FT4X18X10	7	20 L BRKT	27	BKP20125	23
FT4X20X10	7	24 L BRKT	27	BKP20188	23
FT4X24X10	7	90 DEGREE KIT	15	BKW063	23
FT4X30X10	7	7187	49	BKW094	23
FT6X8X10	7	7197	49	BKW125	23
FT6X12X10	7	ARC-37-150	49	BKW188	23
FT6X16X10	7	ARS-37-150	49	BKYH18-094	25
FT6X18X10	7	ARS-37-150SW	49	BKYH18-094-Series	25
FT6X20X10	7	ARW-37-200	49	BKYH30-094	25
FT6X24X10	7	ARW-37-200SW	49	BKYH30-094-Series	25
		ATR1/4X72	48	BTM WASHER	9
		ATR1/4X120	48	BW4	43
		ATR1/4X144	48	CABLE ROLLER	43
		ATR3/8X72	48	CLEANSHEAR	51
		ATR3/8X120	48	CLEANSHEAR BEND	51
		ATR3/8X144	48	CTR HUNG CLP	21
		ATR1/2X72	48	DROP OUT	44
		ATR1/2X120	48	FLEXMATE2	11
		ATR1/2X144	48	FLEXMATE TOOL	11
		ATTACHMENT CLP	29	FTA2DO	44
		B22SGALV120	49	FTA2FS	39
		B22SHGALV120	49	FTA2RS	46
		B56SGALV120	49	FTA4RS	46
		B56SHGALV120	49	FTA6HD	15, 20, 28
		B201	48	FTA6RS	46
		B202	48	FTA9WTK	30
		B409UF-12	38	FTA050CC	29, 45
		B409UF-18	38	FTA075CC	45
		B409UF-21	38	FTA100CC	45
FLEXTRAY™ Covers					
2 IN COVER	41				
4 IN COVER	41				
6 IN COVER	41				
8 IN COVER	41				
12 IN COVER	41				
16 IN COVER	41				
18 IN COVER	41				
20 IN COVER	41				
24 IN COVER	41				

Catalog No.	Page	Catalog No.	Page	Catalog No.	Page
Accessories		Accessories		Accessories	
FTA125CC	45	FTSBK	14	N228	49
FTB2UB	21, 29	FTSCH	10	PEDESTAL CLAMP	37
FTB06CS	27	FTSHAK	15	PEDESTAL KIT	37
FTB06CT	22	FTSTLC	12	RACK CLAMP	45
FTB08CS	27	FTSWN	10	SB301-1/2X8	21
FTB08CT	22	FTU2X6X2	33	SB420ACW	46
FTB12CS	27	FTU2X6X4	33	SB420AFB	46
FTB12CT	22	FTU2X6X10	33	SB420ATG	46
FTB16CS	27	FTU2X12X2	33	SB2204	45
FTB16CT	22	FTU2X12X4	33	SPLICE BAR	13
FTB18CS	27	FTU2X12X10	33	SUPT WASHER	15, 20, 28
FTB18CT	22	FTU2X20X2	33	TOOLLESS CLIP	37, 43
FTB20CS	27	FTU2X20X4	33	TOP WASHER	9
FTB20CT	22	FTU2X20X10	33	TRAPEZE SUPT2	19
FTB24CS	27	FTU4X6X2	33	WASHER SPL KIT	9
FTB24CT	22	FTU4X6X4	33	WB30BC	52
FT BE 2X2	42	FTU4X6X10	33	WB30RB	52
FT BE 2X4	42	FTU4X12X2	33	WB46H	19
FT BE 2X6	42	FTU4X12X4	33	WB48WMK	30
FT BE 2X8	42	FTU4X12X10	33	WB50BA	52
FT BE 2X12	42	FTU4X20X2	33	WB50RB	52
FT BE 2X16	42	FTU4X20X4	33	WB50WC	52
FT BE 2X18	42	FTU4X20X10	33	WB1224WMK	30
FT BE 2X20	42	FTU6X6X2	33	WBU1203	36
FT BE 2X24	42	FTU6X6X4	33	WBU1204	36
FT BE 4X4	42	FTU6X6X10	33	WBU1205	36
FT BE 4X6	42	FTU6X12X2	33	WBU1206	36
FT BE 4X8	42	FTU6X12X4	33	WBU1216	34
FT BE 4X12	42	FTU6X12X10	33	WBU1224	34
FT BE 4X16	42	FTU6X20X2	33	WBU1231	34
FT BE 4X18	42	FTU6X20X4	33	WBU2016	34
FT BE 4X20	42	FTU6X20X10	33	WBU2024	34
FT BE 4X24	42	FTU120404	34	WBU2031	34
FT BE 6X8	42	FTU120608	34	WBUCB8	35
FT BE 6X12	42	FTU200404	34	WBUCB12	35
FT BE 6X16	42	FTU200608	34	WBUCF	36
FT BE 6X18	42	GROUND BOLT	39, 47	WBUCK12	35
FT BE 6X20	42	GROUND SUPT GL	47	WBUCK812	35
FT BE 6X24	42	INSERT 4X118	42	WBUF	39
FTHDWE 1/4	9	INSERT 6X118	42	WBUFA	39
FTS3SP	11	INSERT 8X118	42	WBUFLT	33
FTS12ESK	14	INSERT 12X118	42	WBUFLT-06	33
FTS12SB	14	INSERT 16X118	42	WBUFLT-12	33
FTS20SK	17	INSERT 18X118	42	WBUD	36
FTS21SK	17	INSERT 20X118	42	WBUL16	35
FTS22SK	17	INSERT 24X118	42	WBUL24	35
FTS23SK	17	LABEL CLIP	47	WBUL31	35
FTS24SK	17	N224	49	WBUPC	36
FTS36SB	14	N225	49	WBUTAPE	39
				Z BRKT	28

Eaton's B-Line Business reserves the right to make changes to the specifications, materials, equipment, prices, or the availability of products at any time without prior notice. While every effort has been made to assure the accuracy of information contained in this catalog at the time of publication, we cannot accept responsibility for inaccuracies resulting from undetected errors or omissions.

U.S. Customer Service Center is staffed Monday through Friday
from 7 a.m. to 5:00 p.m. Central Standard Time.

**Eaton's B-Line Business
United States**
509 West Monroe Street
Highland, IL 62249
United States
Phone: (800) 851-7415
www.cooperblines.com/contactus

**Eaton's B-Line Business
Canada**
5925 McLaughlin Road
Mississauga, ON L5R 1B8
Canada
Phone: (800) 569-3660
www.cooperblines.com/contactca

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

B-Line Division
509 West Monroe Street
Highland, IL 62249
Phone: 800-851-7415
Fax: 618-654-1917
www.eaton.com/b-lineseries

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. FLX-15
May 2015 35M

Eaton is a registered trademark
All other trademarks are property
of their respective owners.