



EMT FITTINGS

Aluminum Set-Screw Conduit Bodies . . .	54	Zinc EMT Set-Screw Connectors . . .	71
Aluminum Set-Screw Conduit Bodies (With Cover & Gasket) . . .	57	Zinc EMT Set-Screw Couplings . . .	72
Aluminum Combination Conduit Bodies (With Cover & Gasket) . . .	60	Zinc EMT Compression Connectors . . .	73
Conduit Body Covers and Neoprene Gaskets . . .	63, 64	Zinc EMT Compression Couplings . . .	74
Steel EMT Set-Screw Connectors . . .	65	Combination Couplings . . .	75
Steel EMT Set-Screw Couplings . . .	66	Zinc 90° Pull Elbows . . .	76
Steel EMT Compression Connectors . . .	67	Zinc Offset Connectors . . .	77
Steel EMT Compression Couplings . . .	68	Zinc 90° Corner Pull Elbows and 90° Compression Connectors . . .	78
Steel Raintight EMT Compression Connectors . . .	69	EMT Straps . . .	79
Steel Raintight EMT Compression Couplings . . .	70	Zinc Combination Couplings and Nail Straps . . .	80

Aluminum Set-Screw Conduit Bodies

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.

Standard Materials:

1/2" - 2"

Die Cast/Copper-Free Aluminum

2 1/2" - 4"

Sand-Cast Copper-Free Aluminum

Standard Finish:


Aluminum Enameled



UL Listed:
E198259




TYPE C1AT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
C TYPE										
C1AT	1/2"	4.69	1.38	1.31	N/A	4.35	10	50	21	49015
C2AT	3/4"	5.50	1.56	1.63	3 #6 AWG	7.30	10	50	33	49025
C3AT	1"	6.48	1.88	1.88	3 #4 AWG	12.20	5	25	46	49035
C4AT	1-1/4"	8.31	2.50	2.50	3 #2 AWG	33.50	-	10	82	49045
C5AT	1-1/2"	8.38	2.50	2.50	3 #1/0 AWG	33.50	-	10	85	49055
C6AT	2"	10.31	3.38	3.38	3 #4/0 AWG	69.50	-	5	188	49065
C7AT	2-1/2"	13.12	4.50	4.00	3 #250 MCM	69.50	-	1	325	49075
C8AT	3"	13.19	4.56	4.56	3 #250 MCM	188.00	-	1	399	49085
C9AT	3-1/2"	16.12	5.69	5.63	3 #300 MCM	307.00	-	1	975	49095
C10AT	4"	16.12	5.69	5.63	3 #300 MCM	309.00	-	1	875	49005



TYPE LB1AT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LB TYPE										
LB1AT	1/2"	4.31	1.31	2.19	N/A	4.35	10	50	24	45015
LB2AT	3/4"	5.06	1.56	2.44	3 #6 AWG	7.25	10	50	37	45025
LB3AT	1"	5.87	1.75	2.75	3 #4 AWG	12.20	5	25	46	45035
LB4AT	1-1/4"	7.81	2.50	3.44	3 #2 AWG	32.30	-	10	98	45045
LB5AT	1-1/2"	7.81	2.50	3.44	3 #2 AWG	33.80	-	10	91	45055
LB6AT	2"	10.06	3.12	4.31	3 #4/0 AWG	71.20	-	5	222	45065
LB7AT	2-1/2"	12.81	4.50	5.31	3 #4/0 AWG	71.20	-	1	366	45075
LB8AT	3"	12.81	4.50	5.94	3 #4/0 AWG	183.50	-	1	430	45085
LB9AT	3-1/2"	15.62	5.56	7.06	3 #400 MCM	304.90	-	1	937	45095
LB10AT	4"	15.62	5.56	7.06	3 #400 MCM	308.00	-	1	851	45105

Aluminum Set-Screw Conduit Bodies

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.

Standard Materials:

1/2" - 2"

Die Cast/Copper-Free Aluminum

2 1/2" - 4"

Sand-Cast Copper-Free Aluminum


Standard Finish:

Aluminum Enameled

 **UL Listed:**
E198259




TYPE LL1AT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LL TYPE										
LL1AT	1/2"	4.31	2.06	1.38	N/A	4.35	10	50	25	46015
LL2AT	3/4"	5.06	2.25	1.63	3 #6 AWG	7.30	10	50	37	46025
LL3AT	1"	5.87	2.63	1.88	3 #4 AWG	12.20	5	25	45	46035
LL4AT	1-1/4"	7.81	3.63	2.50	3 #2 AWG	35.80	-	10	98	46045
LL5AT	1-1/2"	7.81	3.63	2.50	3 #1/0 AWG	35.80	-	10	92	46055
LL6AT	2"	10.06	4.44	3.38	3 #4/0 AWG	69.70	-	5	245	46065
LL7AT	2-1/2"	12.81	5.75	4.00	3 #300 MCM	69.70	-	1	388	46066
LL8AT	3"	12.81	5.75	4.50	3 #350 MCM	186.00	-	1	439	46067
LL9AT	3-1/2"	15.62	11.69	5.63	3 #350 MCM	306.00	-	1	924	46068
LL10AT	4"	15.62	11.69	5.63	3 #350 MCM	308.00	-	1	882	46069



TYPE LR1AT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LR TYPE										
LR1AT	1/2"	4.31	2.06	1.38	N/A	4.35	10	50	23	47015
LR2AT	3/4"	5.06	2.25	1.63	3 #6 AWG	7.30	10	50	38	47025
LR3AT	1"	5.87	2.63	1.88	3 #4 AWG	12.20	5	25	49	47035
LR4AT	1-1/4"	7.81	3.63	2.50	3 #2 AWG	35.80	-	10	98	47045
LR5AT	1-1/2"	7.81	3.63	2.50	3 #1/0 AWG	35.80	-	10	94	47055
LR6AT	2"	10.06	4.44	3.38	3 #4/0 AWG	69.70	-	5	254	47065
LR7AT	2-1/2"	12.81	5.75	4.00	3 #300 MCM	69.70	-	1	366	47066
LR8AT	3"	12.81	5.75	4.50	3 #350 MCM	186.00	-	1	406	47067
LR9AT	3-1/2"	15.62	11.69	5.63	3 #350 MCM	306.00	-	1	928	47068
LR10AT	4"	15.62	11.69	5.63	3 #350 MCM	308.00	-	1	902	47069

Aluminum Set-Screw Conduit Bodies

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.

Standard Materials:

1/2" - 2"

Die Cast/Copper-Free Aluminum

2 1/2" - 4"

Sand-Cast Copper-Free Aluminum

Standard Finish:


Aluminum Enameled



UL Listed:
E198259



TYPE T1AT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
T TYPE										
T1AT	1/2"	4.75	2.06	1.38	N/A	4.35	10	50	23	48015
T2AT	3/4"	5.56	2.25	1.63	3 #6 AWG	7.25	10	50	38	48025
T3AT	1"	6.44	2.63	1.88	3 #4 AWG	12.20	5	25	53	48035
T4AT	1-1/4"	8.25	3.56	2.50	3 #2 AWG	33.10	-	10	100	48045
T5AT	1-1/2"	8.38	3.56	2.50	3 #1/0 AWG	33.10	-	10	98	48055
T6AT	2"	10.69	4.38	3.13	3 #4/0 AWG	67.00	-	5	265	48065
T7AT	2-1/2"	13.25	5.75	4.00	3 #4/0 AWG	67.00	-	1	375	48066
T8AT	3"	13.25	5.75	4.50	3 #4/0 AWG	175.00	-	1	444	48067
T9AT	3-1/2"	16.13	7.69	5.63	3 #400 MCM	298.00	-	1	1146	48068
T10AT	4"	16.13	7.69	5.63	3 #400 MCM	300.00	-	1	1079	48069

Aluminum Set-Screw Conduit Bodies with Cover and Gasket

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Assembled with neoprene gasket and stamped cover.

Standard Materials:

1/2" - 2"
Die Cast/Copper-Free
Aluminum

2 1/2" - 4"
Sand-Cast Copper-Free
Aluminum


Standard Finish:

Aluminum Enameled

 **UL Listed:**
E198259




TYPE C1ATCG



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
C TYPE										
C1ATCG	1/2"	4.69	1.38	1.31	N/A	4.35	10	50	21	10400
C2ATCG	3/4"	5.50	1.56	1.63	3 #6 AWG	7.30	10	50	33	10401
C3ATCG	1"	6.48	1.88	1.88	3 #4 AWG	12.20	5	25	46	10402
C4ATCG	1-1/4"	8.31	2.50	2.50	3 #2 AWG	33.50	-	10	82	10403
C5ATCG	1-1/2"	8.38	2.50	2.50	3 #1/0 AWG	33.50	-	10	85	10404
C6ATCG	2"	10.31	3.38	3.38	3 #4/0 AWG	69.50	-	5	188	10405
C7ATCG	2-1/2"	13.12	4.50	4.00	3 #250 MCM	69.50	-	1	325	10406
C8ATCG	3"	13.19	4.56	4.56	3 #250 MCM	188.00	-	1	399	10407
C9ATCG	3-1/2"	16.12	5.69	5.63	3 #300 MCM	307.00	-	1	975	10408
C10ATCG	4"	16.12	5.69	5.63	3 #300 MCM	309.00	-	1	875	10409



TYPE LB1ATCG



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LB TYPE										
LB1ATCG	1/2"	4.31	1.31	2.19	N/A	4.35	10	50	24	10410
LB2ATCG	3/4"	5.06	1.56	2.44	3 #6 AWG	7.25	10	50	37	10411
LB3ATCG	1"	5.87	1.75	2.75	3 #4 AWG	12.20	5	25	46	10412
LB4ATCG	1-1/4"	7.81	2.50	3.44	3 #2 AWG	32.30	-	10	98	10413
LB5ATCG	1-1/2"	7.81	2.50	3.44	3 #2 AWG	33.80	-	10	91	10414
LB6ATCG	2"	10.06	3.12	4.31	3 #4/0 AWG	71.20	-	5	222	10415
LB7ATCG	2-1/2"	12.81	4.50	5.31	3 #4/0 AWG	71.20	-	1	366	10416
LB8ATCG	3"	12.81	4.50	5.94	3 #4/0 AWG	183.50	-	1	430	10417
LB9ATCG	3-1/2"	15.62	5.56	7.06	3 #400 MCM	304.90	-	1	937	10418
LB10ATCG	4"	15.62	5.56	7.06	3 #400 MCM	308.00	-	1	851	10419

Aluminum Set-Screw Conduit Bodies with Cover and Gasket

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Assembled with neoprene gasket and stamped cover.

Standard Materials:

1/2" - 2"
Die Cast/Copper-Free
Aluminum

2 1/2" - 4"
Sand-Cast Copper-Free
Aluminum


Standard Finish:

Aluminum Enameled

 **UL Listed:**
E198259




TYPE LL1ATCG



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LL TYPE										
LL1ATCG	1/2"	4.31	2.06	1.38	N/A	4.35	10	50	25	10440
LL2ATCG	3/4"	5.06	2.25	1.63	3 #6 AWG	7.30	10	50	37	10441
LL3ATCG	1"	5.87	2.63	1.88	3 #4 AWG	12.20	5	25	45	10442
LL4ATCG	1-1/4"	7.81	3.63	2.50	3 #2 AWG	35.80	-	10	98	10443
LL5ATCG	1-1/2"	7.81	3.63	2.50	3 #1/0 AWG	35.80	-	10	92	10444
LL6ATCG	2"	10.06	4.44	3.38	3 #4/0 AWG	69.70	-	5	245	10445
LL7ATCG	2-1/2"	12.81	5.75	4.00	3 #300 MCM	69.70	-	1	388	10446
LL8ATCG	3"	12.81	5.75	4.50	3 #350 MCM	186.00	-	1	439	10447
LL9ATCG	3-1/2"	15.62	11.69	5.63	3 #350 MCM	306.00	-	1	924	10448
LL10ATCG	4"	15.62	11.69	5.63	3 #350 MCM	308.00	-	1	882	10449



TYPE LR1ATCG



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LR TYPE										
LR1ATCG	1/2"	4.31	2.06	1.38	N/A	4.35	10	50	23	10430
LR2ATCG	3/4"	5.06	2.25	1.63	3 #6 AWG	7.30	10	50	38	10431
LR3ATCG	1"	5.87	2.63	1.88	3 #4 AWG	12.20	5	25	49	10432
LR4ATCG	1-1/4"	7.81	3.63	2.50	3 #2 AWG	35.80	-	10	98	10433
LR5ATCG	1-1/2"	7.81	3.63	2.50	3 #1/0 AWG	35.80	-	10	94	10434
LR6ATCG	2"	10.06	4.44	3.38	3 #4/0 AWG	69.70	-	5	254	10435
LR7ATCG	2-1/2"	12.81	5.75	4.00	3 #300 MCM	69.70	-	1	366	10436
LR8ATCG	3"	12.81	5.75	4.50	3 #350 MCM	186.00	-	1	406	10437
LR9ATCG	3-1/2"	15.62	11.69	5.63	3 #350 MCM	306.00	-	1	928	10438
LR10ATCG	4"	15.62	11.69	5.63	3 #350 MCM	308.00	-	1	902	10439

Aluminum Set-Screw Conduit Bodies with Cover and Gasket

For EMT Conduit

Application:

To provide access to conductors for pulling, splicing, and maintenance. Use for thinwall conduit.

Features:

- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Assembled with neoprene gasket and stamped cover.

Standard Materials:

1/2" - 2"

Die Cast/Copper-Free Aluminum

2 1/2" - 4"

Sand-Cast Copper-Free Aluminum


Standard Finish:

Aluminum Enameled

 **UL Listed:**
E198259



TYPE T1ATCG



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
T TYPE										
T1ATCG	1/2"	4.75	2.06	1.38	N/A	4.35	10	50	23	10420
T2ATCG	3/4"	5.56	2.25	1.63	3 #6 AWG	7.25	10	50	38	10421
T3ATCG	1"	6.44	2.63	1.88	3 #4 AWG	12.20	5	25	53	10422
T4ATCG	1-1/4"	8.25	3.56	2.50	3 #2 AWG	33.10	-	10	100	10423
T5ATCG	1-1/2"	8.38	3.56	2.50	3 #1/0 AWG	33.10	-	10	98	10424
T6ATCG	2"	10.69	4.38	3.13	3 #4/0 AWG	67.00	-	5	265	10425
T7ATCG	2-1/2"	13.25	5.75	4.00	3 #4/0 AWG	67.00	-	1	375	10426
T8ATCG	3"	13.25	5.75	4.50	3 #4/0 AWG	175.00	-	1	444	10427
T9ATCG	3-1/2"	16.13	7.69	5.63	3 #400 MCM	298.00	-	1	1146	10428
T10ATCG	4"	16.13	7.69	5.63	3 #400 MCM	300.00	-	1	1079	10429

Aluminum Combination Conduit Bodies With Cover & Gasket

For Threaded Rigid Conduit, IMC and EMT

Application:

Used with threaded rigid conduit, IMC and EMT for providing access to the interior of conduit system for pulling, splicing, inspection and maintenance.

Features:

- Assembled with slotted/Robertson combination screws.
- Assembled with neoprene gasket and stamped cover.
- Tapered threaded hubs (NPT).
- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Suitable for use in concrete.

Standard Materials:

Die cast/Copper-free Aluminum

Standard Finish:


Aluminum Enameled



UL Listed
E198259




Type C1CA



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
C TYPE										
C1CA	1/2"	4.69	1.38	1.56	N/A	4.35	10	50	28	64401
C2CA	3/4"	5.50	1.56	1.75	3 #6 AWG	7.30	10	50	41	64402
C3CA	1"	6.48	1.88	2.13	3 #4 AWG	12.20	5	25	56	64403
C4CA	1-1/4"	8.31	2.50	2.75	3 #2 AWG	33.50	-	10	101	64404
C5CA	1-1/2"	8.38	2.50	2.75	3 #1/0 AWG	33.50	-	10	104	64405
C6CA	2"	10.31	3.38	3.63	3 #4/0 AWG	69.50	-	5	220	64406



Type LB1CA



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LB TYPE										
LB1CA	1/2"	4.31	1.31	2.44	N/A	4.35	10	50	24	64101
LB2CA	3/4"	5.06	1.56	2.69	3 #6 AWG	7.25	10	50	37	64102
LB3CA	1"	5.87	1.75	3.00	3 #4 AWG	12.20	5	25	46	64103
LB4CA	1-1/4"	7.81	2.50	3.69	3 #2 AWG	32.30	-	10	98	64104
LB5CA	1-1/2"	7.81	2.50	3.69	3 #2 AWG	33.80	-	10	91	64105
LB6CA	2"	10.06	3.12	4.56	3 #4/0 AWG	71.20	-	5	222	64106

Aluminum Combination Conduit Bodies With Cover & Gasket

For Threaded Rigid Conduit, IMC and EMT

Application:

Used with threaded rigid conduit, IMC and EMT for providing access to the interior of conduit system for pulling, splicing, inspection and maintenance.

Features:

- Assembled with slotted/Robertson combination screws.
- Assembled with neoprene gasket and stamped cover.
- Tapered threaded hubs (NPT).
- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Suitable for use in concrete.

Standard Materials:


Die cast/Copper-free Aluminum

Standard Finish:

Aluminum Enameled




Type LL1CA



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LL TYPE										
LL1CA	1/2"	4.31	2.06	1.63	N/A	4.35	10	50	25	64201
LL2CA	3/4"	5.06	2.25	1.88	3 #6 AWG	7.30	10	50	37	64202
LL3CA	1"	5.87	2.63	2.13	3 #4 AWG	12.20	5	25	45	64203
LL4CA	1-1/4"	7.81	3.63	2.75	3 #2 AWG	35.80	-	10	98	64204
LL5CA	1-1/2"	7.81	3.63	2.75	3 #1/0 AWG	35.80	-	10	92	64205
LL6CA	2"	10.06	4.44	3.63	3 #4/0 AWG	69.70	-	5	245	64206



Type LR1CA



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
LR TYPE										
LR1CA	1/2"	4.31	2.06	1.63	N/A	4.35	10	50	23	64301
LR2CA	3/4"	5.06	2.25	1.88	3 #6 AWG	7.30	10	50	38	64302
LR3CA	1"	5.87	2.63	2.13	3 #4 AWG	12.20	5	25	49	64303
LR4CA	1-1/4"	7.81	3.63	2.75	3 #2 AWG	35.80	-	10	98	64304
LR5CA	1-1/2"	7.81	3.63	2.75	3 #1/0 AWG	35.80	-	10	94	64305
LR6CA	2"	10.06	4.44	3.63	3 #4/0 AWG	69.70	-	5	254	64306

Aluminum Combination Conduit Bodies With Cover & Gasket

For Threaded Rigid Conduit, IMC and EMT

Application:

Used with threaded rigid conduit, IMC and EMT for providing access to the interior of conduit system for pulling, splicing, inspection and maintenance.

Features:

- Assembled with slotted/Robertson combination screws.
- Assembled with neoprene gasket and stamped cover.
- Tapered threaded hubs (NPT).
- Die cast from high-strength, corrosion and weather resistant, copper-free aluminum alloy.
- Flat back design for easy mounting close to walls.
- Suitable for use in concrete.

Standard Materials:


Die cast/Copper-free Aluminum

Standard Finish:

Aluminum Enameled



UL Listed
E198259



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAXIMUM WIRE SIZE	VOLUME CU. IN.	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
T TYPE										
T1CA	1/2"	4.75	2.06	1.63	N/A	4.35	10	50	23	64501
T2CA	3/4"	5.56	2.25	1.88	3 #6 AWG	7.25	10	50	38	64502
T3CA	1"	6.44	2.63	2.13	3 #4 AWG	12.20	5	25	53	64503
T4CA	1-1/4"	8.25	3.56	2.75	3 #2 AWG	33.10	-	10	100	64504
T5CA	1-1/2"	8.38	3.56	2.75	3 #1/0 AWG	33.10	-	10	98	64505
T6CA	2"	10.69	4.38	3.63	3 #4/0 AWG	67.00	-	5	265	64506

Conduit Body Covers

Steel and Aluminum Covers

Application:

- Used with conduit bodies to cover opening.

Features:

- Assembled with captive zinc plated steel screws.

Standard Materials:

Steel


Standard Finish:

Zinc plated

 **UL Listed:**
E198259



Type 02



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
Steel Covers							
01	1/2"	3.875	1.310	25	250	9	49017
02	3/4"	4.625	1.520	25	250	13	49027
03	1"	5.315	1.710	20	200	19	49037
04	1-1/4" - 1-1/2"	7.240	2.510	25	100	31	49047
05	2"	9.484	3.110	-	50	50	49057
06	2-1/2" - 3"	14.937	5.500	-	10	94	49067
07	3-1/2" - 4"	15.000	6.000	-	10	138	49077

Application:

- Used with conduit bodies to cover opening.

Features:

- Assembled with captive zinc plated steel screws.
- Stamped from high-strength aluminum, corrosion and weather resistant copper-free aluminum alloy.


Standard Materials:

Stamped Aluminum

 **UL Listed:**
E198259



Type 02A



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
Aluminum Covers							
01A	1/2"	3.90	1.37	25	250	6	49105
02A	3/4"	4.70	1.60	25	250	10	49205
03A	1"	5.40	1.78	20	200	14	49305
04A	1-1/4" - 1-1/2"	7.25	2.52	25	100	18	49405
05A	2"	9.50	3.11	-	50	20	49505
06A	2-1/2" - 3"	12.13	4.45	-	10	33	49605
07A	3-1/2" - 4"	14.94	5.50	-	10	62	49705

Conduit Body Covers



Neoprene Gaskets

Application:

- Gasket used with conduit bodies for a raintight seal.

Standard Materials:

Neoprene Rubber



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
Neoprene Gaskets							
10	1/2"	3.90	1.37	200	2000	3	49910
11	3/4"	4.60	1.56	100	1000	3	49911
12	1"	5.34	1.73	100	1000	3	49912
13	1-1/4" - 1-1/2"	7.25	2.51	50	500	6	49913
14	2"	9.50	3.05	25	100	11	49914
15	2-1/2" - 3"	12.13	4.39	-	10	13	49915
16	3-1/2" - 4"	14.88	5.43	-	10	28	49916

Steel EMT Set-Screw Connectors

For EMT Conduit

Application:

To ground and secure E.M.T. raceways to boxes and enclosures.

Features:

- Heavy steel walls
- Concrete tight
- Pre-set/Pre-staked set screws
- Male hub threads NPS
- Three-way combination screws

Standard Materials:

Steel

Standard Finish:


Zinc Plated



UL Listed:
E308075



Type S1111




CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S1110	1/2"	1/2"	0.87	1.53	50	500	9	62007
S1111	3/4"	3/4"	1.10	1.58	25	250	13	62017
S1112	1"	1"	1.36	1.83	50	200	20	62027
*S1112A	1-1/4"	1-1/4"	1.73	2.34	25	100	36	62037
*S1112B	1-1/2"	1-1/2"	1.97	2.27	10	40	45	62047
*S1112C	2"	2"	2.45	2.40	5	20	64	62057
*S1112D	2-1/2"	2-1/2"	3.10	3.18	-	12	130	62067
*S1112E	3"	3"	3.72	3.81	-	12	140	62077
*S1112E1	3-1/2"	3-1/2"	4.24	4.31	-	6	180	62087
*S1112F	4"	4"	4.74	4.87	-	6	225	62097

* Furnished with two set-screws

Insulated Throat



Type S4067



CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S4066	1/2"	1/2"	0.87	1.53	50	500	9	62003
S4067	3/4"	3/4"	1.10	1.58	25	250	13	62013
S4068	1"	1"	1.36	1.83	50	200	20	62023
*S4069	1-1/4"	1-1/4"	1.73	2.34	25	100	36	62033
*S4070	1-1/2"	1-1/2"	1.97	2.27	10	40	45	62043
*S4071	2"	2"	2.45	2.40	5	20	64	62053
*S4072	2-1/2"	2-1/2"	3.10	3.18	-	12	130	62063
*S4073	3"	3"	3.72	3.81	-	12	140	62073
*S4074	3-1/2"	3-1/2"	4.24	4.31	-	6	180	62083
*S4075	4"	4"	4.74	4.87	-	6	225	62093

* Furnished with two set-screws

Steel EMT Set-Screw Couplings

For EMT Conduit

Application:

To ground and secure E.M.T. raceway sections together.

Features:

- Heavy steel walls
- Concrete tight
- Pre-set/Pre-staked set screws
- Three-way combination screws


Standard Materials:

Steel

Standard Finish:

Zinc Plated

 **UL Listed:**
E308075



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
S1113	1/2"	0.87	1.63	50	500	8	62107
S1114	3/4"	1.10	1.86	25	250	13	62117
S1115	1"	1.36	2.31	50	200	20	62127
*S1115A	1-1/4"	1.73	2.76	25	100	40	62137
*S1115B	1-1/2"	1.97	3.00	10	40	58	62147
*S1115C	2"	2.45	3.27	5	20	65	62157
*S1115D	2-1/2"	3.10	4.00	-	12	130	62167
*S1115E	3"	3.72	4.25	-	12	140	62177
*S1115E1	3-1/2"	4.24	4.50	-	6	217	62187
*S1115F	4"	4.74	4.75	-	6	250	62197

* Furnished with four set-screws

Steel EMT Compression Connectors

For EMT Conduit

Application:

To ground and secure E.M.T. raceways to boxes and enclosures.

Features:

- Male hub threads NPS
- Concrete tight
- Heavy Steel Walls

Standard Materials:

Steel

Standard Finish:


Zinc Plated



UL Listed:
E308075



Type S1011




CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S1010	1/2"	1/2"	1.040	0.034	1.120	50	500	11	61007
S1011	3/4"	3/4"	1.040	0.043	1.390	25	250	17	61017
S1012	1"	1"	1.050	0.052	1.700	50	200	23	61027
S1013	1-1/4"	1-1/4"	1.270	0.062	2.050	25	100	41	61037
S1014	1-1/2"	1-1/2"	1.400	0.064	2.250	10	40	50	61047
S1015	2"	2"	1.520	0.066	2.780	5	20	67	61057
S1015D	2-1/2"	2-1/2"	2.510	0.083	3.600	-	12	177	61067
S1015E	3"	3"	2.540	0.083	4.260	-	12	234	61077
S1015E1	3-1/2"	3-1/2"	2.720	0.087	4.710	-	6	288	60187
S1015F	4"	4"	2.890	0.090	5.210	-	6	343	61097

Insulated Throat



Type S4061



CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S4060	1/2"	1/2"	1.040	0.034	1.120	50	500	11	61003
S4061	3/4"	3/4"	1.040	0.043	1.390	25	250	17	61013
S4062	1"	1"	1.050	0.052	1.700	50	200	23	61023
S4063	1-1/4"	1-1/4"	1.270	0.062	2.050	25	100	41	61033
S4064	1-1/2"	1-1/2"	1.400	0.064	2.250	10	40	50	61043
S4065	2"	2"	1.520	0.066	2.780	5	20	67	61053
S4065D	2-1/2"	2-1/2"	2.510	0.083	3.600	-	12	177	61063
S4065E	3"	3"	2.540	0.083	4.200	-	12	234	61073
S4065E1	3-1/2"	3-1/2"	2.720	0.087	4.710	-	6	288	61083
S4065F	4"	4"	2.890	0.090	5.210	-	6	343	61093

Steel EMT Compression Couplings

For EMT Conduit

Application:

To ground and secure E.M.T. raceway sections together.

Features:

- Concrete tight
- Heavy Steel Walls

Standard Materials:

Steel

Standard Finish:


Zinc Plated



UL Listed:
E308075



Type S1017



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
S1016	1/2"	1.60	1.12	50	500	8	61107
S1017	3/4"	1.60	1.39	25	250	13	61117
S1018	1"	1.71	1.68	50	200	20	61127
S1019	1-1/4"	2.08	2.06	25	100	40	61137
S1020	1-1/2"	2.36	2.25	10	40	58	61147
S1021	2"	2.40	2.78	5	20	65	61157
S1021D	2-1/2"	3.89	3.65	-	12	130	61167
S1021E	3"	4.25	4.31	-	12	140	61177
S1021E1	3-1/2"	4.65	4.75	-	6	217	61187
S1021F	4"	4.90	5.27	-	6	250	61197

Steel Raintight EMT Compression Connectors

For EMT Conduit

Application:

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting E.M.T. to box or enclosure.

Features:

- The only steel compression fitting, UL Listed Raintight
- Unique raised bump design affords fast, positive locking of compression nuts
- Male Hub Threads-NPSM
- Steel locknuts
- Heavy steel walls
- Raintight
- Concrete tight

Standard Materials:

Steel


Standard Finish:

Zinc Plated

PATENTED




UL Listed:
E308075



CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S1010RT	1/2"	1/2"	1.040	0.034	1.120	50	500	11	62201
S1011RT	3/4"	3/4"	1.040	0.043	1.390	25	250	17	62202
S1012RT	1"	1"	1.050	0.052	1.700	50	200	23	62203
S1013RT	1-1/4"	1-1/4"	1.270	0.062	2.050	25	100	41	62204
S1014RT	1-1/2"	1-1/2"	1.400	0.064	2.250	10	40	50	62205
S1015RT	2"	2"	1.520	0.066	2.780	5	20	67	62206
S1015DRT	2-1/2"	2-1/2"	2.510	0.083	3.600	-	12	177	62311
S1015ERT	3"	3"	2.540	0.083	4.260	-	12	234	62312
S1015E1RT	3-1/2"	3-1/2"	2.720	0.087	4.710	-	6	288	62313
S1015FRT	4"	4"	2.890	0.090	5.210	-	6	343	62314

Insulated Throat



CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
S4060RT	1/2"	1/2"	1.040	0.034	1.120	50	500	11	62301
S4061RT	3/4"	3/4"	1.040	0.043	1.390	25	250	17	62302
S4062RT	1"	1"	1.050	0.052	1.700	50	200	23	62303
S4063RT	1-1/4"	1-1/4"	1.270	0.062	2.050	25	100	41	62304
S4064RT	1-1/2"	1-1/2"	1.400	0.064	2.250	10	40	50	62305
S4065RT	2"	2"	1.520	0.066	2.780	5	20	67	62306
S4065DRT	2-1/2"	2-1/2"	2.510	0.083	3.600	-	12	177	62307
S4065ERT	3"	3"	2.540	0.083	4.260	-	12	234	62308
S4065E1RT	3-1/2"	3-1/2"	2.720	0.087	4.710	-	6	288	62309
S4065FRT	4"	4"	2.890	0.090	5.210	-	6	343	62310

Steel Raintight EMT Compression Couplings

For EMT Conduit

Application:

Compression style coupling used to join two lengths of E.M.T. Internal sealing rings create a raintight seal.

Features:

- The only steel compression fitting, UL Listed Raintight
- Unique raised bump design affords fast, positive locking of compression nuts
- Heavy steel walls
- Raintight
- Concrete tight

Standard Materials:

Steel

Standard Finish:

Zinc Plated


PATENTED



UL Listed:
E308075



Type S1017RT



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
S1016RT	1/2"	1.60	1.12	50	500	8	62401
S1017RT	3/4"	1.60	1.39	25	250	13	62402
S1018RT	1"	1.71	1.68	50	200	20	62403
S1019RT	1-1/4"	2.08	2.06	25	100	40	62404
S1020RT	1-1/2"	2.36	2.25	10	40	58	62405
S1021RT	2"	2.40	2.78	5	20	65	62406
S1021DRT	2-1/2"	3.89	3.65	-	12	130	62407
S1021ERT	3"	4.25	4.31	-	12	140	62408
S1021E1RT	3-1/2"	4.65	4.75	-	6	217	62409
S1021FRT	4"	4.90	5.27	-	6	250	62410

Zinc EMT Set-Screw Connectors

For EMT Conduit

Application:

To secure and terminate E.M.T. to knockouts in concrete tight box or dry location applications.

Features:

- Concrete tight
- Pre-set/pre-staked set-screws
- Combination head set-screws
- Male hub threads NPS

Standard Materials:


Zinc Die Cast



UL Listed:
E308075




Type 1111




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1110	1/2"	1.16	0.41	50	500	7	62002
1111	3/4"	1.31	0.47	25	250	10	62012
1112	1"	1.56	0.56	50	200	15	62022
*1112A	1-1/4"	1.96	0.63	25	100	29	62032
*1112B	1-1/2"	2.19	0.72	10	40	40	62042
*1112C	2"	2.50	0.75	5	20	54	62052
*1112D	2-1/2"	3.03	1.00	-	12	83	62062
*1112E	3"	3.37	1.06	-	12	100	62072
*1112E1	3-1/2"	3.58	1.09	-	10	128	62082
*1112F	4"	3.75	1.09	-	6	156	62092

*Furnished with two set-screws

Insulated Throat



Type 4067



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
4066	1/2"	1.16	0.41	50	500	7	62008
4067	3/4"	1.31	0.47	25	250	10	62018
4068	1"	1.56	0.56	50	200	15	62028
*4069	1-1/4"	1.96	0.63	25	100	29	62038
*4070	1-1/2"	2.19	0.72	10	40	40	62048
*4071	2"	2.50	0.75	5	20	54	62058
*4072	2-1/2"	3.03	1.00	-	12	83	62068
*4073	3"	3.37	1.06	-	12	100	62078
*4074	3-1/2"	3.58	1.09	-	10	128	62088
*4075	4"	3.75	1.09	-	6	156	62098

*Furnished with two set-screws

Zinc EMT Set-Screw Couplings

For EMT Conduit

Application:

To ground and secure E.M.T. raceway sections together.

Features:

- Heavy steel walls
- Concrete tight
- Pre-set/Pre-staked set screws
- Three-way combination screws

Material/Finish:


Zinc Die Cast



UL Listed:
E308075



Type 1114



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1113	1/2"	1.53	0.94	50	500	8	62102
1114	3/4"	1.88	1.16	25	250	13	62112
1115	1"	2.00	1.43	50	200	20	62122
*1115A	1-1/4"	2.50	1.84	25	100	40	62132
*1115B	1-1/2"	2.88	2.07	10	40	58	62142
*1115C	2"	3.44	2.55	5	20	65	62152
*1115D	2-1/2"	3.99	3.30	-	12	130	62162
*1115E	3"	4.55	3.94	-	12	140	62172
*1115E1	3-1/2"	4.82	4.45	-	10	217	62182
*1115F	4"	5.24	4.97	-	6	250	62192

*Furnished with four set-screws

Zinc EMT Compression Connectors

For EMT Conduit

Application:

To secure and terminate E.M.T. to knockouts in concrete tight box, dry or damp location applications.

Features:

- Male hub threads NPS
- Concrete tight

Standard Materials:


Zinc Die Cast



UL Listed:
E308075



Type 1011




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1010	1/2"	1.20	0.40	50	500	10	61002
1011	3/4"	1.27	0.40	25	250	14	61012
1012	1"	1.48	0.50	50	200	20	61022
1013	1-1/4"	1.75	0.59	25	100	37	61032
1014	1-1/2"	1.91	0.62	10	40	55	61042
1015	2"	2.11	0.76	5	20	81	61052
1015D	2-1/2"	2.62	1.00	-	12	107	61062
1015E	3"	2.75	1.06	-	12	137	61072
1015E1	3-1/2"	2.83	1.14	-	10	176	61082
1015F	4"	2.84	1.14	-	6	206	61092

Insulated Throat



Type 4061



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
4060	1/2"	1.20	0.40	50	500	10	61008
4061	3/4"	1.27	0.40	25	250	14	61018
4062	1"	1.48	0.50	50	200	20	61028
4063	1-1/4"	1.75	0.59	25	100	37	61038
4064	1-1/2"	1.91	0.62	10	40	55	61048
4065	2"	2.11	0.76	5	20	81	61058
4065D	2-1/2"	2.62	1.00	-	12	107	61068
4065E	3"	2.75	1.06	-	12	137	61078
4065E1	3-1/2"	2.83	1.14	-	10	176	61088
4065F	4"	2.84	1.14	-	6	206	61098

Zinc EMT Compression Couplings

For EMT Conduit

Application:

To join lengths of E.M.T. for concrete tight, dry or damp location applications.

Features:

- Concrete tight

Standard Materials:


Zinc Die Cast



UL Listed:
E308075



Type 1017



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1016	1/2"	1.59	1.09	50	500	8	61102
1017	3/4"	1.81	1.28	25	250	13	61112
1018	1"	1.82	1.60	50	200	20	61122
1019	1-1/4"	2.07	2.00	25	100	40	61132
1020	1-1/2"	2.47	2.29	10	40	58	61142
1021	2"	2.56	2.79	5	20	65	61152
1021D	2-1/2"	3.29	3.51	-	12	130	61162
1021E	3"	3.42	4.21	-	12	140	61172
1021E1	3-1/2"	3.51	4.75	-	10	217	61182
1021F	4"	3.54	5.32	-	6	250	61192

Combination Couplings

For Rigid Conduit, IMC and E.M.T.

Application:

To join E.M.T. to Rigid or IMC

Features:

- Threaded rigid and IMC to compression E.M.T.
- Concrete tight
- NPT female hub

Standard Materials:

Steel

Standard Finish:


Zinc Plated

 **UL Listed:**
E198258

For EMT Steel Compression to Threaded Rigid Couplings



Type ERC-23



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	DIM D	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
ERC-22	1/2"	1.313	1.125	0.875	0.688	25	250	14	47322
ERC-23	3/4"	1.438	1.375	1.125	0.750	25	250	25	47323
ERC-24	1"	1.500	1.688	1.375	0.813	25	250	34	47324

Application:

A combination coupling to provide a transition from EMT to unthreaded rigid conduit or IMC.

Features:

- Pre-set and staked Robertson head screws
- Concrete tight when taped

Standard Materials:

Steel

Standard Finish:


Zinc Plated

 **UL Listed:**
E198258

For EMT Steel Set-Screw to Rigid Set-Screw Couplings



Type S18ES



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	DIM D	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
S16ES	1/2"	1.000	2.375	0.875	0.938	50	500	14	23016
S17ES	3/4"	1.250	2.813	1.125	1.125	25	250	28	23017
S18ES	1"	1.500	3.000	1.188	1.188	-	25	36	23018

Zinc 90° Pull Elbows

For EMT Conduit

Application:

90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of E.M.T. The removable cover gives ample access so that wire pulling can be achieved without any obstructions.

Feature:

- Removable aluminum cover and neoprene gasket facilitate wire pulling

Standard Materials:

Zinc Die Cast



UL Listed:

E198258
CSA File No. LR57925



Application:

Used to connect E.M.T. conduit to a metal box enclosure at a 90° bend.

Features:

- Removable aluminum cover and neoprene gasket facilitate wire pulling
- Assembled with zinc die cast locknut

Standard Materials:

Zinc Die Cast



UL Listed:


E198258
CSA File No. LR57925



Female to Female



Type 1326




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1326	1/2"	1.31	0.94	10	100	24	13262
1327	3/4"	1.59	1.22	5	50	37	13272
1328	1"	1.94	1.59	-	25	68	13282
1329	1-1/4"	2.36	1.97	-	20	102	13292

Male to Female



Type 1332



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1332	1/2"	1.31	0.93	10	100	22	13322
1333	3/4"	1.47	1.22	5	50	35	13332

Zinc Offset Connectors

For EMT Conduit

Application:

Use to connect E.M.T. conduit to a metal outlet box or enclosure where an offset is desired.

Features:

- Set-Screw Type
- Concrete tight
- Assembled with zinc die cast locknut

Standard Materials:

Zinc Die Cast



UL Listed:
E198256
CSA File No. LR57925



Application:

Use to connect E.M.T. conduit to a metal outlet box or enclosure where an offset is desired.

Features:

- Compression Type
- Raintight & Concrete tight
- Assembled with zinc die cast locknut

Standard Materials:

Zinc Die Cast




UL Listed:
E198256
CSA File No. LR57925



Set-Screw




Type 1250




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1250	1/2"	2.090	0.940	0.375	10	100	12	61250
1251	3/4"	2.980	1.160	0.750	10	100	19	61251

Compression



Type 1260



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1260	1/2"	2.130	1.000	0.375	20	200	13	13761
1261	3/4"	2.900	1.190	0.750	10	100	21	13702

Zinc 90° Corner Pull Elbows and 90° Comp. Conn.

For EMT Conduit

Application:

Similar to that for 90° Corner Pulling Elbows, however, these products are used where it is essential to make tight turns within limited available space.

Features:

- Assembled with tri-combo screws

Standard Materials:

Zinc Die Cast



UL Listed:

E198258


CSA File No. LR57925



Set-Screw



Type 1341




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
1341	1/2"	1.81	1.00	10	100	20	13413	13413
1342	3/4"	1.00	1.25	5	50	29	13423	13423

Male to Female



Type 10E



Application:

Compression type 90° E.M.T. connectors used to terminate E.M.T. to an unthreaded box or enclosure.

Features:

- Concrete tight

Standard Materials:

Zinc Die Cast



UL Listed:

E198258

CSA File No. LR57925



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
10E	1/2"	1.75	0.83	0.52	25	250	20	62101
11E	3/4"	1.86	0.95	0.52	20	200	26	62111
12E	1"	2.21	1.12	0.67	10	100	46	62121

EMT Straps

For EMT Conduit

Application:

Click-on type one-hole straps for E.M.T. Provides support for the conduits, as required by the National Electrical Code.

Standard Materials:

Steel

Standard Finish:

Zinc Plated




UL Listed:
E198338

One-Hole



Type 143S




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	DIM D	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
142S	1/2"	1.720	0.700	0.550	0.312	100	1000	2	81427
143S	3/4"	1.980	0.975	0.630	0.312	100	1000	3	81437
144S	1"	2.210	1.090	0.750	0.312	50	500	4	81447
145S	1-1/4"	2.880	1.540	0.880	0.355	50	500	10	81457
146S	1-1/2"	3.140	1.750	0.990	0.335	-	50	16	81467
147S	2"	3.890	2.150	1.110	0.450	-	50	22	81477
158S	2-1/2"	4.925	2.825	1.245	0.550	-	25	62	81587
159S	3"	5.540	3.430	1.250	0.550	-	25	76	81597
160S	3-1/2"	6.260	3.900	1.250	0.575	-	10	120	81607
161S	4"	6.830	4.390	1.240	0.575	-	10	125	81613

Two-Hole



Type 2143S



Application:

Snap-on type two-hole straps for E.M.T. are used where higher load bearing supports are desired.

Standard Materials:

Steel

Standard Finish:

Zinc Plated



UL Listed:
E198338

CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	DIM D	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
2142S	1/2"	2.200	0.790	0.560	0.200	-	250	1	21427
2143S	3/4"	2.700	0.980	0.620	0.200	-	200	2	21437
2144S	1"	2.975	1.185	0.690	0.200	-	100	4	21447
2145S	1-1/4"	3.650	1.535	0.750	0.275	-	50	5	21457
2146S	1-1/2"	4.250	1.765	0.870	0.275	-	50	8	21467
2147S	2"	4.730	2.300	0.995	0.325	-	25	13	21477
2158S	2-1/2"	6.025	2.855	0.985	0.345	-	25	20	21533
2159S	3"	6.460	3.425	0.995	0.345	-	20	25	21597
2160S	3-1/2"	7.300	3.925	0.990	0.345	-	10	33	21535
2161S	4"	7.895	4.435	0.995	0.345	-	10	36	21617

Zinc Combination Couplings and Nail Straps

For EMT Conduit and Flexible Metallic Conduit

Application:

A combination coupling to provide a transition from E.M.T. to flexible metallic conduit.

Features:

- Assembled with tri-combo screws

Standard Materials:

Zinc Die Cast




UL Listed:

E198256

CSA File No. LR57925



Type 170C



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
*170C	1/2" E.M.T. - 3/8" Flex	1.280	1.140	50	500	8	51702
171C	1/2" E.M.T. - 1/2" Flex	1.645	1.340	25	250	10	51703
172C	3/4" E.M.T. - 3/4" Flex	1.975	1.535	20	200	15	51704
173C	1" E.M.T. - 1" Flex	2.285	1.700	10	100	26	51705

*EMT TO NM CABLE

Application:

A combination coupling to provide a transition from E.M.T. to flexible metallic conduit.

Features:

- Assembled with tri-combo screws

Standard Materials:

Zinc Die Cast




UL Listed:

E198256

CSA File No. LR57925



Type 171



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
171	1/2" E.M.T. - 1/2" FMC	1.645	1.340	25	250	10	51712
172	3/4" E.M.T. - 3/4" FMC	1.975	1.535	20	200	15	51722

Nail Straps for Threaded Rigid Conduit, IMC and EMT Conduit

Application:

To secure rigid to wooden structure members. Use in place of one hole straps.

Features:

- Tensile strength of Cast Steel is 30% higher than Malleable Iron
- Withstands greater striking force

Standard Materials:

Cast Steel

Standard Finish:

Zinc Plated



Type 360M

CATALOG NUMBER	CONDUIT SIZES THINWALL	RIGID	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
360M	1/2"	3/8"	100	1000	3	83607
361M	3/4"	1/2"	100	1000	4	83617
362M	1"	3/4"	100	1000	6	83627