

Effective March 2019

# Residential and light commercial distribution products





Residential	and	light	commercial	products
-------------	-----	-------	------------	----------

# Residential and light commercial products

# **Contents**

Description	Page
Type BR Main Breaker plug-in loadcentres	5
Combination (main circuit breaker) single-phase Type 1	6
Combination (main circuit breaker) single-phase Type 3R	7
Combination (main circuit breaker) three-phase Type 1	8
Combination (main circuit breaker) three-phase Type 3R	9
Type BR Main Lug plug-in loadcentres	5
Non-combination (main lug only) single-phase Type 1	10
Non-combination (main lug only) single-phase Type 3R	11
Non-combination (main lug only) three-phase Type 1	12
Non-combination (main lug only) three-phase Type 3R	13
Non-combination (main lug only) 70 A single-phase	14
Type BR plug-in loadcentre Accessories	15
Plug-in circuit breakers for CPM/CPL/CBRPM/CBRPL	16
Type BR, DNPL, GFTCB, GFEP and GFXB	16
Type BR single- and multi-pole	17
Type DNPL Duplex, Independent Quadplex and circuit breaker packs	18
Type BR arc fault circuit interrupter	19
Types GFCB and GFEP ground fault	20
Type BR internationally rated	22
Types GFXB internationally rated ground fault and Type BR moulded case switches	22
Plug-in loadcentre main circuit breakers for BR	
Types CSR and CC	23
Plug-in circuit breaker accessories for BR loadcentres	
Plug-in OEM loadcentre interior assemblies	25
Type CH plug-in loadcentres	29
Combination and non-combination single-phase	31
Plug-in circuit breakers for CH	31
Type CH single-, multi-pole and twin	31
Type CHP commercial	32
Type CHP arc fault circuit interrupter	33
Type CHP ground fault	
Plug-in loadcentre main circuit breakers for CH	
Type CSR	
Plug-in loadcentres and circuit breaker accessories for CH	
Type CH accessories	36

# Residential and light commercial products

# Contents (continued)

Description	Page
Type CBM/CBL bolt-on loadcentres	37
Combination (main circuit breakers) single- and three-phase aluminum bus	37
Combination (main circuit breakers) single- and three-phase copper bus	38
Non-combination (main lug only) single- and three-phase aluminum bus	39
Non-combination (main lug only) single- and three-phase copper bus	40
Bolt-on circuit breakers for CBM/CBL	41
Type BAB and QBHW single- and multi-pole	41
Type QBA arc fault circuit interrupter and DNBA duplex	42
Type QBGF and QBGFEP ground fault	43
Bolt-on loadcentre and circuit breaker accessories	44
Manual transfer switches/generator panels	45
Spa panels	47
Surge suppression products	49
Stage 1 and Stage 1 Type 2	48
Accessories	49
Street lighting panels	50
In-pole	50
Pedestal	52
Combined loadcentre and meter socket	52
Metered temporary ground fault power panel	53
Mini-power centres	54
Plug-in mini-power centres	55
Plug-in	55
Bolt-on mini-power centres	56
Bolt-on	
Residential fuse panel inserts	
Insert interiors	
Trims	
Replacement classic circuit breakers	
Bolt-on Type BQL single-, multi-pole, Duplex and Quadplex	
Bolt-on Type BQL ground fault and moulded case switches	
Bolt-on Type QBH single- and multi-pole	62
Plug-in Type BJ two- and three-pole	
Pressure switches	64
Index	65

#### **Product description**

Loadcentres feature factory installed main lugs or main breakers. The BR interiors are manufactured of formed, plated aluminum. Eaton also supplies a full line of Eaton brand BR, DNPL, GFTCB and GFEP type branch circuit breakers and accessories for these loadcentres.

## **Product application**

Designed for the protection and distribution of single and multidwelling residential and light commercial loads to 120/240 volts AC, such as lighting, heating, appliance and small motor branch circuits.

All main breaker combination loadcentres are CSA listed for use as service entrance equipment.

## **Ratings**

Single-phase, three-wire, 120/240 volts AC and three-phase, four-wire, 120/208 volts AC. Mains through 400 A. Available with up to 84 branch circuits. Main breakers on 150 and 200 A panels are rated at 25,000 AIC.

## Metal enclosure specifications

Enclosures are made of 16 gauge sheet steel, either galvanized or epoxy painted. These coatings provide superior corrosion protection. All trims used on BR loadcentres are chromate sealed and finished with an electro-disposition epoxy paint in grey (ANSI-61) or white, which exceeds requirements for outdoor and indoor applications. A combination surface/flush cover with integral door is supplied with indoor loadcentres rated from 100 through 400 A.

All plug-in loadcentres are CSA listed to file LL98266. CSA certified to C22.2 No.29.

#### Warranty

10 year limited.

## Type BR loadcentre features and benefits:

Optimized knockout locations for additional access.

Fasier to remove

White box trim and barriers provide more professional look and feel.

Smooth case edges.

2/0 lug is easily removeable and can be installed in any location on the neutral bar.

Inboard neutral increases gutter space to allow for professional installation of conductors.


BR short-body configuration maximizes gutter space providing ease of installation of conductors.

Reduced clutter of pigtails provides a clean gutter space.

Quicker and neater installation, along with a consistent form and fit.

Extra ground positions provided in panels with more than 20 circuits allows guicker and easier wiring.

Self-levelling tabs allow for quick drywall offset.



Commercial grade 25 kAIC series rated main breaker with lock-off bracket for superior protection.

Common screws minimize the number of tools required for installation. Neutral bar, ground bar, and BR breaker screws share a common drive type.

Bonding screw provides a quick and easy means of bonding the ground and neutral.

Plug-on neutral (PON) eliminates the pigtail connection providing time and labour savings for a professional installation.

Backed out neutral and ground screws allow for quick connection of neutral and ground conductors.

#### Cover features include:

Improved twist-outs that are easier to remove


Durable embossed circuit numbering with added marking for twin breakers


Keyhole hanging feature allows for easier cover installation


## Combination (main circuit breaker) single-phase Type 1

Three-wire, 120/240 Vac combination service entrance Type 1 (indoor)









Product selection

## Table 1a. Main circuit breaker indoor Type 1 BR plug-on neutral loadcentres

Maximum	Main	0.11	Max. no.	Max. no.	•	Type .	Dimension	ns (inches)		
ampere rating	breaker rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover style	of main breaker	Н	w	D	Wire size range for main CU/AL
125	100	CBRPM112	12	24	Flush/surface	BRH a	18-3/4	14-3/8	3-7/8	#8-1/0
125	100	CBRPM116	16	32	Flush/surface	BRH a	21	14-3/8	3-7/8	#8-1/0
125	125	CBRPM116Z	16	32	Flush/surface	BRH b	21	14-3/8	3-7/8	#4-2/0
125	100	CBRPM120	20	40	Flush/surface	BRH a	27	14-3/8	3-7/8	#8-1/0
125	100	CBRPM130	30	60	Flush/surface	BRH a	29-1/8	14-3/8	3-7/8	#8-1/0
125	125	CBRPM130Z	30	60	Flush/surface	BRH b	29-1/8	14-3/8	3-7/8	#4-2/0
125	100	CBRPM140	40	80	Flush/surface	BRH a	34-1/8	14-3/8	3-7/8	#8-1/0
125	125	CBRPM140Z	40	80	Flush/surface	BRH b	34-1/8	14-3/8	3-7/8	#4-2/0
150	150	CBRPM1520	20	40	Flush/surface	CSR c	29-1/8	14-3/8	3-7/8	#2-300 MCM
150	150	CBRPM1530	30	60	Flush/surface	CSR c	34-1/8	14-3/8	3-7/8	#2-300 MCM
150	150	CBRPM1540	40	80	Flush/surface	CSR c	39	14-3/8	3-7/8	#2-300 MCM
200	200	CBRPM216	16	32	Flush/surface	CSR c	29-1/8	14-3/8	3-7/8	#2-300 MCM
200	200	CBRPM220	20	40	Flush/surface	CSR c	29-1/8	14-3/8	3-7/8	#2-300 MCM
200	200	CBRPM230	30	60	Flush/surface	CSR c	34-1/8	14-3/8	3-7/8	#2-300 MCM
200	200	CBRPM240	40	80	Flush/surface	CSR c	39	14-3/8	3-7/8	#2-300 MCM
200	200	CBRPM260	60	120	Flush/surface	CSR c	49	14-3/8	3-7/8	#2-300 MCM

Table 1b. Main circuit breaker indoor Type 1 BR non plug-on neutral loadcentres

Maximum	Main	0-4-1	Max. no.	Max. no.	0	Type	Dimension	ns (inches)		18/:
ampere rating	breaker rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover style	of main breaker	Н	w	D	Wire size range for main CU/AL
400	300	CPM342	42	84	Flush/surface	DK q	66-1/2	16-1/8	6-5/16	(2)#2/0-250 MCM or (1)#2/0-500 MCM f
400	400	CPM442	42	4 <u>2</u> f	Flush/surface	DK q	66-1/2	16-1/8	6-5/16	(2)#2/0-250 MCM or (1)#2/0-500 MCM f

a High Interrupting 22 kAIC BRH breakers

b 22 kAIC BRH2125 main breaker is factory installed.

c Factory installed 25 kAIC main breaker.


d DK breaker is a 65 kAIC, factory-sealed breaker.

e Restricted due to available neutrals, extra neutrals are available on page 15 table 10b which will expand available circuitry to a maximum of 84 circuits.

f 3TA401K must be ordered separately for #2/0-500-MCM.

# Combination (main circuit breaker) single-phase Type 3R

Three-wire 120/240 Vac combination service entrance Type 3R (outdoor/raintight) a



RCPM220

Table 2. Main circuit breaker outdoor/raintight Type 3R loadcentres a

Maximum	Main	0-4-1	Max. no.	Max. no.	0	Type of main	Dimension	ns (inches)		Wire size
ampere rating	breaker rating		1-inch spaces	1/2-inch spaces	Cover style	breaker	н	w	D	range for main Cu/Al
125	100	RCPM112 b	12	24	Outdoor	BR cd	18-1/2	14-3/8	5	#8-1/0
125	100	RCPM120 b	20	40	Outdoor	BR cd	25	14-3/8	5	#8-1/0
125	100	RCPM130 b	30	60	Outdoor	BR cd	28-7/8	14-3/8	5	#8-1/0
150	150	RCPM1530 b	30	60	Outdoor	CSR e	33-7/8	14-3/8	5	#2-300 MCM
200	200	RCPM220 b	20	40	Outdoor	CSR e	28-7/8	14-3/8	5	#2-300 MCM
200	200	RCPM230 b	30	60	Outdoor	CSR e	33-7/8	14-3/8	5	#2-300 MCM
200	200	RCPM240 b	40	80	Outdoor	CSR e	38-3/4	14-3/8	5	#2-300 MCM

a Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See page 15 table 10b for selection.

b All enclosures include a locking hasp as an integral part of the door latching mechanism.

c Type BR—100 A 10 kAIC main circuit breaker is factory installed (BR2100).


d High interrupting BRH breakers are available on page 17.


e Factory installed 25 kAIC main breaker.

# Combination (main circuit breaker) three-phase Type 1

Four-wire 120/208 Vac combination service entrance Type 1 (indoor)







3CPM112

3CPM130

Table 3. Main circuit breaker indoor Type 1 loadcentres

Maximum	Main	0.11	Max. no.	Max. no.		Type .	Dimension	ons (inches)		Wire size
ampere rating	breaker rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover style	of main breaker	Н	w	D	main Cu/Al
125	100	3CPM112	12	24	Flush/surface	BR bc	21	14-3/8	3-3/4	#4-1/0
125	100	3CPM130	30	60	Flush/surface	CC d	39	14-3/8	3-3/4	#4-4/0
200	200	3CPM230	30	60	Flush/surface	CC d	39	14-3/8	3-3/4	#1-250 MCM
400	400	<b>3CPM442</b> a	42	42 a	Flush/surface	DK e	66-1/2	16-1/8	6-5/16	(2) 2/0–250 MCM (1) 2/0–500 MCM f

a Extra neutrals which will expand available circuitry to a maximum of 84 circuits are available on page 15.

b Type BR—100 A 10 kAIC main circuit breaker is factory installed (BR3100).

c High interrupting BRH breakers are available on page 17...

d Factory installed 10 kAIC main breaker.

e DK Breaker is a 65 kAIC factory-sealed main breaker.

f Circuit breaker lug kit 3TA401 must be ordered separately to accept #2/0-500 MCM cabling.

# Combination (main circuit breaker) three-phase Type 3R

Four-wire 120/208 Vac combination service entrance Type 3R (outdoor/raintight) ab




Table 4. Main circuit breaker outdoor/raintight Type 3R loadcentres ab

Maximum	Main	0-4-1	Max. no.	Max. no.	0	Туре	Dimensio	ns (in)		Wire size
ampere rating	breaker rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover style	of main breaker	Н	w	D	range for main Cu/Al
100	100	R3CPM112 b	12	24	Outdoor	BR cd	20-3/4	14-3/8	5	#4-1/0
125	100	R3CPM130 b	30	60	Outdoor	CC e	38-3/4	14-3/8	5	#4-4/0
200	200	R3CPM230 b	30	60	Outdoor	CC e	38-3/4	14-3/8	5	#1-250 MCM

a Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See page 15 for selection.

b All enclosures include a locking hasp as an integral part of the door latching mechanism.

c Type BR—100 A 10 kAIC main circuit breaker is factory installed (BR3100).

d High interrupting BRH breakers are available on page 17.


e Factory installed 10 kAIC main breaker.

# Type BR plug-in main lug loadcentres

# Non-combination (main lug only) single-phase Type 1

Three-wire 120/240 Vac non-combination Type 1 (indoor)







CBRPL120

# Product selection

Table 5a. Main lug only indoor Type 1 loadcentres

Maximum		Max. no.	Max. no.		Dimensio	ns (inches)		Wire size	
Ampere Rating	Catalogue Number	1-inch spaces	1/2-inch spaces	Cover style	Н	w	D	range for main Cu/Al	
125	CBRPL112	12	24	Flush/surface	16-3/4	14-3/8	3-7/8	#14-2/0	
125	CBRPL116	16	32	Flush/surface	18-3/4	14-3/8	3-7/8	#14-2/0	
125	CBRPL120	20	40	Flush/surface	21	14-3/8	3-7/8	#14-2/0	
125	CBRPL130	30	60	Flush/surface	29-1/8	14-3/8	3-7/8	#14-2/0	
200	CBRPL220	20	40	Flush/surface	27	14-3/8	3-7/8	#1-300 MCM	
200	CBRPL240	40	80	Flush/surface	34-1/8	14-3/8	3-7/8	#1-300 MCM	

Table 5b. Main lug only indoor Type 1 non plug-in loadcentres.


Maximum		Max. no.	Max. no.		Dimensio	ns (inches)		Wire size
Ampere Rating	Catalogue Number	1-inch spaces	1/2-inch spaces	Cover style	Н	w	D	range for main Cu/Al
100	CCPL102	2 a	4	Surface	11-1/2	6-3/4	3-1/4	#14-1/0
125	CCPL104	4	8	Flush/surface	13	11	3-1/2	#14-2/0
125	CCPL108	8	16	Flush/surface	13	11	3-1/2	#14-2/0
400	CPL442	42	42 ь	Flush/surface	54	16-1/8	6-5/16	(1) 250–750 MCM (2) 3/0–250 MCM


 $<sup>\</sup>boldsymbol{a}$  Service equipment approved when used with two-pole BR type breaker.

b Extra neutrals which will expand available circuitry to a maximum of 84 circuits are available on page 15

# Non-combination (main lug only) single-phase Type 3R

Three-Wire 120/240 Vac non-combination Type 3R (outdoor/raintight) a





RCPL220

Table 6. Main lug only outdoor/raintight Type 3R loadcentres a

Maximum	0.41	Max. no.	Max. no.		Dimension	ns (inches)		Wire size
ampere rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover Style	Н	w	D	range for main Cu/Al
125	RCCPL102 b	2 c	4	Outdoor	11-1/2	6-1/2	4	#14-2/0
125	RCCPL104 b	4	8	Outdoor	13	11	3-1/2	#14-2/0
125	RCCPL108 b	8	16	Outdoor	13	11	3-1/2	#14-2/0
125	RCPL112 b	12	24	Outdoor	16-1/2	14-3/8	5	#14-2/0
125	RCPL120 b	20	40	Outdoor	20-3/4	14-3/8	5	#14-2/0
125	RCPL130 b	30	60	Outdoor	28-7/8	14-3/8	5	#14-2/0
200	RCPL220 b	20	40	Outdoor	25	14-3/8	5	#1-300 MCM
200	RCPL240 b	40	80	Outdoor	33-7/8	14-3/8	5	#1-250 MCM

a Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See page 15 for selection.


b All enclosures include a locking hasp as an integral part of the door latching mechanism.


 $c\,$  Service equipment approved when used with two-pole BR type breaker.


# Type BR plug-in main lug loadcentres

# Non-combination (main lug only) three-phase Type 1

Four-wire 120/208 Vac non-combination Type 1 (indoor)







3CPL112 3CPL224 3CPL124

Table 7. Main lug only indoor Type 1 loadcentres


Maximum		Max. no.	Max. no.	_	Dimensio	ns (inches)		Wire size
ampere rating	Catalogue number	1-inch spaces	1/2-inch spaces	Cover style	Н	w	D	range for main Cu/Al
100	3CCPL103	3 а	6	Surface	14-1/4	6-1/2	3-1/4	#14-2/0
125	3CPL112	12	24	Flush/surface	21	14-3/8	3-7/8	#8-2/0
125	3CPL124	24	48	Flush/surface	29	14-3/8	3-7/8	#8-2/0
125	3CPL130	30	60	Flush/surface	34.12	14-3/8	3-7/8	#8-2/0
125	3CPL136	36	72	Flush/surface	39	14-3/8	3-7/8	#8-2/0
200	3CPL218	18	36	Flush/surface	27	14-3/8	3-7/8	#2-300 MCM
200	3CPL224	24	48	Flush/surface	34.12	14-3/8	3-7/8	#2-300 MCM
200	3CPL230	30	60	Flush/surface	34.12	14-3/8	3-7/8	#2-300 MCM
200	3CPL242	42	84	Flush/surface	39	14-3/8	3-7/8	#2-300 MCM
400	3CPL442	42	42 b	Flush/surface	54	16-3/8	6-5/16	(1) 250–750 MCM (2) 3/0–250 MCM


a Suitable for use as service equipment when used with three-pole BR type breaker.

b Extra neutrals which will expand available circuitry to a maximum of 84 circuits are available on page 15.

# Non-combination (main lug only) three-phase Type 3R

Four-wire 120/208 Vac non-combination Type 3R (outdoor/raintight) a





R3CPL230

Table 8. Main lug only outdoor/raintight Type 3R Loadcentres a

Maximum	0-4-1	Max. no.	Max. no.	0	Dimensions (inches)			Wire size	
ampere rating	Catalogue number		1/2-inch spaces	Cover style	н	w	D	range for main Cu/Al	
100	R3CCPL103 b	3 с	_	Outdoor	11-1/2	6-1/2	4	#14-2/0	
125	R3CPL112 b	12	24	Outdoor	20-3/4	14-3/8	5	#14-2/0	
125	R3CPL130 b	30	60	Outdoor	38-3/4	14-3/8	5	#14-2/0	
125	R3CPL136 b	36	72	Outdoor	38-3/4	14-3/8	5	#14-2/0	
200	R3CPL230 b	30	60	Outdoor	33-7/8	14-3/8	5	#2-300 MCM	
200	R3CPL242 b	42	42 d	Outdoor	38-3/4	14-3/8	5	#2-300 MCM	

a Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See page 15 for selection.

b All enclosures include a locking hasp as an integral part of the door latching mechanism.

 $<sup>\</sup>ensuremath{c}$  Suitable for use as service equipment when used with three-pole BR type breaker.


d Extra neutrals to expand available circuitry to a maximum of 84 circuits are available on  ${f page}$  15.

# Type BR plug-in main lug loadcentres

# Non-combination (main lug only) 70 A single-phase

Three-wire 250 Vac maximum non-combination

Service entrance approved when used with two-pole BR or BRH breakers. a











CPL072 indoor

CPL072R c outdoor

CPL072FGP flush

CPL072SGP surface

CPL072RGP cd outdoor

Table 9. 70 A main lug only polymeric and metallic loadcentres

Maximum				Max. no.		Dimensions (inches)			Wire size
ampere rating	Enclosure style	Catalogue Material number	1-inch spaces	1/2-inch spaces	н	w	D	range for main Cu/Al	
70	Indoor Type 1 b	Polymeric	CPL072	2	4	8-5/8	5	3-1/4	#14-2
70	Indoor/outdoor Type 3R b	Polymeric	CPL072R c	2	4	8-11/16	6-1/4	4-5/16	#14-2
70	Indoor Type 1 flush mount b	Metallic	CPL072FGP	2	4	9-7/16	4-1/2	3	#14-2
70	Indoor Type 1 surface mount b	Metallic	CPL072SGP	2	4	9-7/16	4-1/2	3	#14-2
70	Indoor/outdoor Type 3R b	Metallic	CPL072RGP cd	2	4	9-7/16	4-1/2	3	#14-2

a BR and BRH two-pole breakers can be found on page 17.

b Service entrance approved when used with two-pole BR/BRH breakers.

c The circuit breaker protective cover incorporates a locking hasp.

d Uses DS\*H1 style hubs found on  $\boldsymbol{page}$  15.

# Type BR plug-in loadcentre accessories

Table 10a. Type BR Plug-on Neutral (PON) loadcenter CBRPM/CBRPL accessories

Description	Catalogue number
White cover replacement latch—indoor loadcenters	LATCHPW
Grey cover replacement latch—indoor loadcenters	LATCHPG
Retaining bracket for backfed main breaker—BR	BRPHD
Hold down screw for 2 pole type BJ in BR PON loadcentre	BRPHDBJ
Incoming 2/0 neutral lug	NLP20
Incoming 300 kcmil neutral lug	NLP300
BR loadcenter panel directory label 0-30 circuits a	LCPD30
BR loadcenter panel directory label 0-40 circuits a	LCPD40
BR loadcenter panel directory label 31-60 circuits a	LCPD60

Description	number
Bonding kit for bonding the neutral bus to the loadcenter	BONDKITP
5 terminal ground bar kit	GBKP5
10 terminal ground bar kit	GBKP10
14 terminal ground bar kit	GBKP14
21 terminal ground bar kit	GBKP21
225A/2P subfeed lug block - #2-300KCMIL	BRPSF225
(1) 42 cct panel label, (6) white panel cover screws, (3) filler plates, (1) Eaton arc flash label, (1) neutral or ground lug	BRPNLKIT

## Table 10b. Legacy Plug-in loadcenter CPM/CPL accessories

Description	Catalogue number
Number strips for CPL/CPM 42 circuits a	NSP42
Circuit identification labels (e.g. hot water heater) b	BP3110C
Ground bar kit 5 position	GBK5
Ground bar kit 8 position	GBK8
Ground bar kit 10 position	GBK10
Ground bar kit 14 position	GBK14
Ground bar kit 21 position	GBK21
Subfeed kit for 125 A loadcentres #8–2/0 g	BRSF125
Subfeed kit for 150 A three-phase loadcentres #8–2/0 g	3BRSF150
Subfeed kit for 225 A loadcentres #2-300 MCM g	BRS225
Subfeed kit for 225 A three-phase loadcentres #2-300 MCM g	3BRS225
Subfeed kit for 400 A loadcentres #8-300 MCM g	BRS400
Subfeed kit for 400 A three-phase loadcentres g	3BRS400
Neutral/ground lug kit for 2/0 h	NL20
Neutral/ground lug kit for 3/0 h	NL30
Neutral/ground lug kit for 300 MCM (maximum) h	NL300
Neutral kit for 400 A combination loadcentres i	CPM400KIT
Neutral kit for 400 A non-combination loadcentres j	CPL400KIT
White plastic replacement door latch	52-3125-6
White spray can touch up paint	SPCWH

Description	Catalogue number
Door lock for 4-8 circuit 125 A (CPM/CPL)	CH9FL k
Door lock for 12–42 circuit 100–225 A and 400 A (CPM/CPL)	TDL k
Isolated ground kit	ISGRD
Trim screw kit (CPM/CPL) d	CVRSCRW
Trim screw kit white (order in quantities of 25)	LCCSW
3/4-inch hub for 100–125 A Type 3R loadcentres (3 x 2-3/4 inches) e	DS075H1
1-inch hub for 100–125 A Type 3R loadcentres (3 x 2-3/4 inches) e	DS100H1
1-1/4 inch hub for 100-125 A Type 3R loadcentres (3 x 2-3/4 inches) e	DS125H1
1-1/2 inch hub for 100–125 A Type 3R loadcentres (3 x 2-3/4 inches) e	DS150H1
2-inch hub for 100–125 A Type 3R loadcentres (3 x 2-3/4 inches) e	DS200H1
2-inch hub for 150 and 200 A Type 3R loadcentres (4-3/4 x 4-5/8 inches)	DS200H2
2-1/2 inch hub for 150 and 200 A Type 3R loadcentres (4-3/4 x 4-5/8 inches	DS250H2
3-inch hub for 150 and 200 A Type 3R loadcentres (4-3/4 x 4-5/8 inches)	DS300H2
3/4-inch hub for R3CCPL103 loadcentres (2-1/8 x 3-1/4 inches)	RH75P
1-inch hub for R3CCPL103 loadcentres (2-1/8 x 3-1/4 inches)	RH100P
1-1/4 inch hub for R3CCPL103 loadcentres (2-1/8 x 3-1/4 inches) RH125P	RH125P
1-inch filler plate kit f	BRFP
Grey plastic replacement door latch	52-3125-5
Grey spray can touch up paint	SPC61

a 25 per package. Catalogue number represents one package.

b 50 per package. Catalogue number represents one package.

 $<sup>\</sup>boldsymbol{c}$  Includes outer trim only, no door, and no deadfront.

 $d\ 100$  per package. Catalogue number represents one package.

e Except R3CCPL103.

f Kit includes 25 pieces.

g Line/Load terminals supplied only. Neutral conductor must be purchased separately. See above listed kits.

h Neutral bolts to main neutral bar i.e. remove screw and install lug kit.

i Kit includes 2 neutral bars.

j Kit includes 1 neutral bar.

k Comes with a set of keys.

## Type BR, DNPL, GFTCB, GFEP, and GFXB

#### BR circuit breakers

Eaton Type BR plug-in breakers in the standard 1-inch per pole moulded case and can be used as main and/or branch disconnect devices. All are CSA and UL listed. Typical ampacity range for BR breakers is 15 through 125 A.

#### FIRE-GUARD arc fault circuit interrupter (AFCI)

The FIRE-GUARD arc fault circuit interrupter (AFCI) is a residential circuit breaker with an integrated processor which recognizes the unique current and/or voltage signatures associated with arcing faults, and acts to interrupt the circuit to reduce the likelihood of an electrical fire. With the Eaton Fire-Guard AFCI, protection from arcing faults is combined with conventional thermal and magnetic overloads as found in standard residential circuit breakers protecting wiring from excessive heat or damage due to overloading or short circuits. Fire-Guard AFCI can also be equipped with 5 mA ground fault protection to protect from personal shock hazards. Now, there is a residential circuit breaker that provides protection from arcing faults, conductor damage due to thermal overloads and short circuits, as well as 5 mA ground fault protection in one integrated design.

## GFTCB people protection breakers

Eaton Type GFCB (ground fault circuit breaker) combines state-ofthe-art electronic technology with a circuit breaker mechanism in a compact 1-inch per pole moulded case. The GFCB automatically senses hot wire-to-ground faults in a 4 to 6 mA range and shuts off the power thus providing an extra margin of safety beyond that of conventional circuit breakers. GFCB applications include bathrooms, basement outlets, swimming pools, outdoor branch circuits and kitchen branch circuits. Self testing compliant to new codes. Type GFCB breakers are also available in 30 mA equipment protectors. 30 mA breakers are for equipment requiring a higher interrupting value such as heat tracing.

#### DNPL twin circuit breakers


DNPL plug-in breakers have the same construction as Eaton Type BR 1-inch per pole devices except that two single-pole circuits are provided in a 1-inch space. CSA listed interrupting rating is 10,000 AIC. All ratings are CSA and UL listed.

### DNPL quad circuit breakers

Quadplex construction of Eaton Type DNPL plug-in breakers provides various combinations of two-pole and single-pole devices in a 2-inch moulded case. All plug-in breakers are approved for HACR applications.

- · All ratings are CSA and UL listed
- CSA certified to C22.2 No. 5, file LR3300
- · All loadcentre breakers are GOS listed for conformity

① Single-pole 15 and 20 A units are switching duty (SWD) rated



## Type BR single- and multi-pole

Type BR ab

- 10,000/22,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac
- Two- and three-pole versions feature a common trip







BR320

BR215

Table 11. Single- and multi-pole plug-in circuit breakers

#### Catalogue numbers

		Outaiogue iiu	IIIDEIG					
Ampere	Wire size	Single-pole, 120/240 Vac 10 per shelf carton		Two-pole, 120 5 per shelf ca	Two-pole, 120/240 Vac 5 per shelf carton		Three-pole, 120/240 Vac 5 per shelf carton	
rating	range (Cu/Al 60 °C or 75 °C)	10 kAIC	22 kAIC	10 kAIC	22 kAIC	10 kAIC	22 kAIC	
15	#14-4	<b>BR115</b> cd	BRH115	BR215	BRH215	BR315	BRH315	
20	#14-4	BR120 cd	BRH120	BR220	BRH220	BR320	BRH320	
25	#14-4	BR125 c	BRH125	BR225	BRH225	BR325	BRH325	
30	#14-4	BR130 c	BRH130	BR230	BRH230	BR330	BRH330	
35	#14-4	BR135 c	BRH135	BR235	BRH235	BR335	BRH335	
40	#14-4	BR140 c	BRH140	BR240	BRH240	BR340	BRH340	
45	#14-4	_	BRH145	BR245	BRH245	BR345	BRH345	
50	#14-4	BR150 c	BRH150	BR250	BRH250	BR350	BRH350	
60	#8-1/0	<b>BR160</b> c	BRH160	BR260	BRH260	BR360	BRH360	
70	#8-1/0	BR170 c	BRH170	BR270	BRH270	BR370	BRH370	
80	#8-1/0	_	_	BR280	BRH280	BR380	BRH380	
90	#8- 1/0	_	_	BR290	BRH290	BR390	BRH390	
100	#8-1/0	_	_	BR2100	BRH2100	BR3100	BRH3100	
110	#8- 1/0	_	_	_	_	_	_	
125	#4-2/0 e	_	_	BR2125 e	_	e	_	
150	e	_	_	e	_	e	_	
175	e	_	_	е	_	e	_	
200	e	_	_	e	_	e	_	
		Requires one 1-	Inch (25.4 mm) space	Requires two 1-	Inch (25.4 mm) spaces	Requires three	1-Inch (25.4 mm) spaces	
		Requires one 1-	Inch (25.4 mm) space	Requires two 1-	Inch (25.4 mm) spaces	Requires three	1-Inch (25.4 i	

a All Type BR single-, two-, and three-pole circuit breakers carry listing for HACR application..

b Breaker shunt trips are available but only in 120 Vac format. Addition of a shunt trip adds a 1-inch space width. For circuit breakers requiring a shunt trip add an ST suffix to the end of the catalogue number (e.g. BR115ST).

c Available with high magnetic setting for switching large tungsten lamp loads. Add suffix H to catalogue number (e.g. BR115H).

d Switching duty rated

e For subfeed applications in 200 or 400 A loadcentres requiring a 125, 150, 175, or 200 A subfeed circuit breaker a Type BJ circuit breaker can be used. Refer to **page 63** for product space requirements and selection.

# Type DNPL Duplex™, Independent Quadplex™ and circuit breaker packs


Type DNPL ab


• 10,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac

Table 12. Duplex and Independent Trip Quadplex plug-in circuit breakers

Duplex 2 single-pole circuits 10 per shelf carton			independent trip ble circuits and 1 two-pole circuit f carton			Quadplex independent trip 2 two-pole circuits 5 per shelf carton			
120 Vac		120 Vac	120/240 Vac	120 Vac		120/240 Vac			
Ampere rating	Catalogue number	Outer left (single-pole) ampere rating	Centre (two-pole) ampere rating	Outer right (single-pole) ampere rating	Catalogue number	Outer left and right (two-pole) ampere rating	Centre (two-pole) ampere rating	Catalogue number	Wire size range (Cu/AI 60 °C or 75 °C)
15–15	DNPL1515	15	15	15	DNPL151515	15	15	DNPL215215	#14-4 AWG
15–20	DNPL1520	15	20	15	DNPL152015	15	20	DNPL215220	#14-4 AWG
15-30	DNPL1530	15	25	15	DNPL152515	15	30	DNPL215230	#14-4 AWG
20-20	DNPL2020	15	30	15	DNPL153015	15	40	DNPL215240	#14-4 AWG
	_	15	40	15	DNPL154015	20	20	DNPL220220	#14-4 AWG
_	_	15	50	15	DNPL155015	20	30	DNPL220230	#14-4 AWG







Requires one 1.00 inch (25.4 mm) space

Independent trip requires two 1.00 inch (25.4 mm) spaces

Independent trip requires two 1.00 inch (25.4 mm) spaces

b All 15 and 20 A single-pole are switch-duty rated.

## Type BP (circuit breaker packs)

- Single carton packaged
- · Represents common household combinations







DNPL155015



DNPL230230

## Table 13. Plug-in circuit breaker house packs

Contents	Catalogue number
(3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP2
(10) BR115, (3) BR215, (1) BR230, (1) BR240	BP4
(2) DNPL1515, (1) DNPL215215, (1) DNPL152015, (1) DNPL153015, (1) DNPL154015	BP16
(6) DNPL1515, (2) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP18
(1) DNPL1515, (3) DNPL151515, (2) DNPL153015, (1) DNPL154015	BP21
(3) DNPL1515, (3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP23
(16) BR115, (3) BR215, (1) BR230, (1) BR240	BP24
(14) BR115, (2) BR120, (1) BR230, (1) BR240	BP27
(5) DNPL1515, (1) DNPL2020, (1) DNPL153015, (1) DNPL154015	BP31
(1) BR120, (4) DNPL1515, (1) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP32
(10) BR115, (2) BR120, (1) BR215, (1) BR220, (1) BR230, (1) BR240	BP41
(3) DNPL1515, (1) DNPL153015, (1) DNPL154015, (1) DNPL2020, (1) DNPL1520	BP54

a All Type DNPL Duplex and Quadplex circuit breakers carry listing for HACR applications.

## Type BR arc fault circuit interrupter

Type BR arc fault circuit interrupter circuit breakers

• 10,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac

An arc fault circuit interrupter is a device intended to provide protection from the effects of arc faults by recognizing characteristics unique to arcing and by functioning to de-energize the circuit when the arc fault is detected. As of January 1, 2015, the Canadian Electrical Code now requires that all branch circuits that supply 125 V, single-phase, 15 and 20 A receptacle outlets installed in dwelling unit shall be protected by a combination arc fault circuit interrupter(s) (series arc and parallel arc detection).

Table 14. Single- and two-pole plug-in AFCI circuit breakers

		Catalogue number			
		Plug-on Neutral Breaker <sup>e</sup>	Pigtail Breaker		
Ampere rating	Configuration	Single-pole 120/240 Vac 20 per shelf carton 10 kAIC		Two-pole <sup>a</sup> 120/240 Vac 5 per shelf carton 10 kAIC	Wire size range (Cu/AI 60 °C or 75 °C)
15	Combination	BRP115AFC d	BRN115AFC d	BRL215CAF bc	#14-4 AWG
15	High interrupting 22 kAIC		BRHN115AF	_	#14-4 AWG
20	Combination	BRP120AFC d	BRN120AFC d	BRL220CAF bc	#14-4 AWG
20	High interrupting 22 kAIC		BRHN120AF	_	#14-4 AWG
		Requires one 1.00 inch (25.4 mm) space		Requires two 1.00 inch (25.4 mm) spaces	

a Common trip refers to two-pole 240 V load application sourced by 120/240 Vac (see Figure 2).

e Only for use in the Type BR plug-on neutral style of combination and non-combination loadcentres




Figure 1. Single-pole, single 120 V load application sourced by 120/240 Vac




Figure 2. Two-pole, 240 V load application sourced by 120/240 Vac



Type BR combination AFCI circuit breaker



Type BR dual purpose AF/GF breaker



Type BR fire alarm breaker features red handle

## Table 15. Single-pole plug-in dual purpose AF/GF breakers

		Pon Breaker b	Pigtail Breaker
Ampere rating	Configuration	Single-pole, 120/2 10 per shelf carto Catalogue numbe	240 Vac n, 10 kAIC r
15	CAFCI / 5 mA GF	BRP115DFC a	BRN115DFC a
20	CAFCI / 5 mA GF	BRP120DFC a	BRN120DFC a
Compact body breaker		Requires one 1.00 inc	ch (25.4 mm) space

a CSA marked only

## Table 16. Single-pole plug-in fire alarm breakers

Ampere rating	Configuration	Single-pole, 120/240 Vac 10 per shelf carton, 10 kAIC Catalogue number
15	Branch fire alarm	BRF115
20	Branch fire alarm	BRF120
	Compact body breaker	Requires one 1.00 inch (25.4 mm) space

b Will not fit into CPM112, CPL112, CPL116, CPL120, CPL220, CPL240, 3CPM112, 3CPL218, 3CPL224 or 3CPL230 prior to November 2004.

c Long style circuit breakers. Please speak to your local Eaton sales rep for proper application.

d CSA marked only

b Only for use in the Type BR plug-on neutral style of combination and non-combination loadcentres

# Types GFCB and GFEP ground fault

## Type GFCB and GFEP ground fault circuit breakers

- 10,000/22,000 A interrupting capacity at 120 Vac and 120/240 Vac
- 5 mA "people protection", or 30 mA equipment protectors
- Two-pole version features common trip





GFTCB single-pole

GFTCB two-pole

#### Table 17. (5 mA) single- and two-pole plug-in ground fault circuit breakers

		Catalogue number						
	Wine eine nemme	Single-pole, 120 Vac 1 per shelf carton	e, 10 kAIC	Two-pole, 120/2 1 per shelf cart	Two-pole, 120/240 Vac 1 per shelf carton			
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Plug-on Breaker d 10 kAIC	Pigtail Breaker 10 kAIC	22 kAIC	10 kAIC	22 kAIC		
15	#14-8	BRP115GFC c	BRN115GFC a c	BRHN115GF	GFTCB215	GFTCBH215		
20	#14-8	BRP120GFC c	BRN120GFC a c	BRHN120GF	GFTCB220	GFTCBH220		
25	#14-8	_	BRN125GFC c	BRHN125GF	GFTCB225	GFTCBH225		
30	#14-8	_	BRN130GFC c	BRHN130GF	GFTCB230	GFTCBH230		
40	#14-8	_	_		GFTCB240	_		
50	#14-8	_	_		GFTCB250 b	_		
60	#14-4	_	_		GFTCB260	_		
		Requires one 1.00 inch (	25.4 mm) space	·	Requires two 1.00	inch (25.4 mm) spaces		

a Auxiliary switches and bell alarms are available under special order with legacy part number (GFTCB115 and GFTCB120). Add suffix W1 for alarm switch and W2 for auxiliary switch.

Table 18. (30 mA) single- and two-pole plug-in ground fault circuit breaker equipment protectors

		Pigtail Breaker			
Ampere	Wire size range Cu/Al 60 °C or	Single-pole, 120 Vac, 1 per shelf carton	Two-pole, 120/240 Vac 1 per shelf carton		
rating	75 °C (AWG)	10 kAIC	10 kAIC		
15	#14-8	BRN115EP	GFEP215		
20	#14-8	BRN120EP	GFEP220		
25	#14-8	BRN125EP	GFEP225		
30	#14-8	BRN130EP	GFEP230		
40	#14-8	_	GFEP240		
50	#14-8	_	GFEP250 a		
		Requires one 1.00 inch (25.4 mm) space	Requires two 1.00 inch (25.4 mm) spaces		

a For use with copper wire only.

## Ground fault application note

Single-pole ground fault circuit breakers (GFCBs) are designed for use in two-wire, 120 Vac circuits. **Figure 3** shows a typical wiring configuration. Two-pole GFCBs are designed for use in three-wire, 120/240 Vac circuits, 120 Vac multi-wire circuits employing common, neutral and two-wire, 240 Vac circuits obtained from a 120/240 Vac source. **Figure 4** and **Figure 6** illustrate typical wiring configurations for 120/240 Vac multi-wire circuits. **Figure 5** depicts a 240 Vac, two-wire circuit.

**Note:** The "panel neutral" conductor connects to the neutral bar, even though the neutral is not included in the load circuit. This connection is necessary to supply a 120 Vac power source to the ground fault sensing circuit. The figures are shown with a 120/240 Vac, single-phase, three-wire power source, but are also applicable to a 120/208 Vac, three-phase, four-wire power supply. For all figures, the electrical operation of the GFCB is not affected by the equipment ground.




Figure 3. Single-pole




Figure 4. Two-pole




Figure 5. Two-pole




Figure 6. Two-pole

b For use with copper wire only.

c CSA marked only.

d Only for use in the Type BR plug-on neutral style of combination and non-combination loadcentres.

# Type BR internationally rated

Type BR internationally rated circuit breakers

- **3000/6000 A** interrupting capacity at 240/415 Vac
- Two- and three-pole versions feature common trip





BR215E



BR320E

BR120E

Table 19. Single-, two-, and three-pole plug-in internationally rated circuit breakers ab

iabic	is. Single-, two-, and	tillee-pole plug-ill	internationally	rateu circuit t	JI Cake
		Catalogue number			

	Wire size range Cu/Al 60 °C or	Catalogue number						
Ampere		Single-pole, 240/415 Vac 10 per shelf carton		Two-pole, 24 5 per shelf ca	0/415 Vac arton	Three-pole, 240-415 Vac 5 per shelf carton		
rating	75 °C (AWG)	3 kAIC	6 kAIC	3 kAIC	6 kAIC	3 kAIC	6 kAIC	
15	#14-4	BR115E	BRH115E	BR215E	BRH215E	BR315E	BRH315E	
20	#14-4	BR120E	BRH120E	BR220E	BRH220E	BR320E	BRH320E	
25	#14-4	BR125E	BRH125E	BR225E	BRH225E	BR325E	BRH325E	
30	#14-4	BR130E	BRH130E	BR230E	BRH230E	BR330E	BRH330E	
35	#14-4	BR135E	BRH135E	BR235E	BRH235E	BR335E	BRH335E	
40	#14-4	BR140E	BRH140E	BR240E	BRH240E	BR340E	BRH340E	
45	#14-4	_	BRH145E	BR245E	BRH245E	BR345E	BRH345E	
50	#14-4	BR150E	BRH150E	BR250E	BRH250E	BR350E	BRH350E	
60	#4-1/0	BR160E	BRH160E	BR260E	BRH260E	BR360E	BRH360E	
70	#4-1/0	BR170E	BRH170E	BR270E	BRH270E	BR370E	BRH370E	
80	#4-1/0	_	_	BR280E	BRH280E	BR380E	BRH380E	
90	#4-1/0	_	_	BR290E	BRH290E	BR390E	BRH390E	
100	#4-1/0	_	_	BR2100E	BRH2100E	BR3100E	BRH3100E	
		Requires one 1.	.00 inch (25.4 mm) space	Requires two 1.	.00 inch (25.4 mm) spaces	Requires three	1.00 inch (25.4 mm) spaces	

a Built to British Standard BS3871.

Table 20. Duplex, 2 single-pole circuits, 240/415 Vac

Ampere rating	Catalogue number			
15–15	DNPL1515E			
15–20	DNPL1520E			
20–20	DNPL2020E			
_	_			
_	_			
Requires one 1.00 inch (25.4 mm) space				

b Non-stocked item requiring special order. Speak to your local Eaton sales rep for lead times.

## Type GFXB internationally rated ground fault and Type BR moulded case switches

Type GFXB internationally rated ground fault circuit breakers

• 3000 A interrupting capacity at 120/240 Vac, 220/380 Vac, and 240/415 Vac



Type GFXB

Table 21. 30 mA single-pole plug-in ground fault circuit breakers abc

		Catalogue number a
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Single-pole, 120 Vac 1 per shelf carton 3 kAIC
15	#14-4	GFXB115B2
20	#14-4	GFXB120B2
25	#14-4	GFXB125B2
30	#14-4	GFXB130B2
		Requires one 1.00 inch (25.4 mm) space

a Auxiliary switches and bell alarms are available under special order. Add suffix W1 for alarm switch and W2 for auxiliary switch.

## Type BR non-automatic moulded case switches



BR250NA

Table 22. Two-pole plug-in non-automatic moulded case switches a

	Wire size range	Catalogue number a
Ampere rating	Cu/AI 60 °C or 75 °C (AWG)	Two-pole, 120/240 Vac 5 per shelf carton
50	#4-1/0	BR250NA
60	#4-1/0	BR260NA
100	#4-1/0	BR2100NA
		Requires two 1.00 inch (25.4 mm) spaces

a Non-stocked part requiring special ordering. Speak to your local Eaton sales rep for lead times.

b Meets requirements of BS3871 section 31C and BS4293.

c Non-stocked part requiring special ordering. Speak to your local Eaton sales rep for lead times.

# Plug-in loadcentre main circuit breakers for BR

# Type CSR, and CC

## Type CSR loadcentre main circuit breaker kit

• 25,000 A interrupting capacity at 120/240 Vac



CSR2150N

Table 23. Two-pole main circuit breakers for single-phase plug-in combination loadcentres

		Catalogue number		
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C	Two-pole, 120/240 Vac 1 per shelf carton 25 kAIC		
125	#2 AWG-300 kcmil	CSR2125N		
150	#2 AWG-300 kcmil	CSR2150N		
200	#2 AWG-300 kcmil	CSR2200N		

Type CC loadcentre main circuit breaker kit



CC3150

Table 24. Three-pole main circuit breakers for three-phase plug-in combination loadcentres

		Catalogue number
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C	Three-pole, 120/240 Vac 1 per shelf carton 10 kAIC
100	#4 AWG-4/0 AWG	CC3100
125	#2 AWG-300 kcmil	CC3125
150	#2 AWG-300 kcmil	CC3150
200	#2 AWG-300 kcmil	CC3200

# Plug-in circuit breaker accessories for BR loadcentres

## Plug-in circuit breaker accessories







BHLW2-10



BRQLW-10



BHLW-10



MCBPL (installed)



THOW-10 (installed)

Table 25. Field installation kits and parts for plug-in loadcentre circuit breakers

Description	Ordering quanity <sup>a</sup>	Catalogue number
Handle tie for single-pole Type BR circuit breakers. Joins handles on breakers mounted adjacent to each other via a clip-on mechanism.	1	BQHT-10
Handle tie for Type DNPL circuit breakers. Joins the two outside independent poles on two adjacent duplex or one quadplex circuit breakers.	1	THOW-10
Handle tie for Type DNPL circuit breakers. Joins the outside independent poles on adjacent duplex or quadplex circuit breakers.	1	THS1
Handle lockoff (escutcheon mounted). Single-, two-, or three-pole Type BR; single-pole of a Type DNPL duplex or; one independent outside pole of a Type DNPL quadplex circuit breakers.	1	BRLW-10
Handle lockoff (handle mounted). Single-pole Type BR circuit breakers. b	1	BRLW1-10
Handle lockoff (handle mounted). Two- and three-pole Type BR circuit breakers. b	1	BRLW2-10
Handle lockoff (handle mounted). Single-pole Type DNPL quadplex circuit breakers. b	1	BRDL1-10
Handle lockoff (escutcheon mounted). Two-pole Type DNPL quadplex circuit breakers. b	1	BRQLW-10
Handle lockoff (screw mounted). Locks the handle of main circuit breaker types CC and CHH in the OFF or ON position. b	1	CCPL
Handle lockoff (escutcheon mounted). Locks the handle of main circuit breaker type CSR and BWH in the OFF of ON position. b	1	MCBPL
Handle lockdog (escutcheon mounted). Single-, two-, and three-pole Type BR; single-pole of a Type DNPL duplex or; one independent pole of a Type DNPL quadplex circuit breaker. Secures handle in the ON or OFF position. b	1	BHLW-10
Handle lockdog (handle mounted). Single-pole Type BR circuit breakers. Secures handle in the ON or OFF position. b	1	BHLW1-10
Handle lockdog (handle mounted). Two- and three-pole Type BR circuit breakers. Secures handle in the ON or OFF position. b	1	BHLW2-10
Handle lockdog (handle mounted). Single-pole Type GFCB ground fault circuit breakers. Secures handle in the ON or OFF position. b	1	BHGW-10
Handle lockdog (handle mounted). Single-pole Type DNPL duplex or 1 outside independent pole of a quadplex. Secures handle in the ON or OFF position. b	1	HLW1-10
Main breaker lug kit. Types CC and CHH circuit breakers (2) 300 kcmil	1	CCL300
Main breaker lug kit. Types CSR, BW, and BWH circuit breakers (2) 300 kcmil	1	MCBL300
Electronic breaker lockoff (escutcheon mounted): Type BR long body AF/GF	1	BRLAFGFLOFF
Electronic breaker lockoff (escutcheon mounted): Type BR compact body AF	1	BRCAFLOFF

a Must be purchased in multiples of ordering quantities indicated.

## **Definitions**

Handle ties: Devices used to join two similar independent single-pole circuit breakers to form a two-pole non-common trip breaker.

Handle lockoffs: Devices that use a padlock to lock a circuit breaker's handle in either the ON or OFF position.

Handle lockdogs: Devices used to secure a circuit breaker's handle in the ON or OFF position. They are not padlockable devices.

Escutcheon mounted: A semipermanent mounting to the face of the circuit breaker and secured by the loadcentre's deadfront cover.

Handle mounted: A mounting made directly to the handle of the circuit breaker by means of a set screw.

Screw mounted: A permanent mounting to the face of the circuit breaker by means of a non-removable screw.

b Refer to your local Eaton sales representative for handle position changeability chart.

#### **Product description**

As a leader in the electrical distribution equipment business, Eaton has a unique product offering for equipment manufacturers, panel builders and virtually any OEM that has a need for power distribution within their equipment. The OEM interior offering consists of a wide variety of power distribution options utilizing components from Eaton's BR Loadcentre product lines. With high-volume, standardized products, OEMs can expect to receive high-quality products covering configurations meeting virtually any power distribution need.

Coupled with Eaton's expertise in circuit breaker design and manufacturing, our OEM interiors provide solid power distribution and circuit protection in a compact, easy-to-install package.

#### **Product offering**

The BR interiors are manufactured of formed, plated aluminum, and use the Eaton Type BR 1.00 inch (25.4 mm) wide circuit breaker by Eaton. This design affords customers the most circuit flexibility as many of these interiors allow the installation of standard single- and two-pole breakers as well duplex (two-pole in a 1.00 inch (25.4 mm) space) or quadplex (four-pole in a 2.00 inch (50.8 mm) space) breakers. The stab rating of the BR interiors is 140 A maximum, meaning that the handle rating of the breakers that are mounted across from one another may not exceed 140 A.

The interiors are designed for either horizontal (single-row breaker mounting), or vertical (double-row breaker mounting).

### Standards and certifications

## Canadian Standards Association listing

All single- and two-pole, 120/240 V breakers, both 1-inch (25.4 mm), 1/2-inch (12.7 mm) and 3/4-inch (19.1 mm) per pole, 225 A maximum, are listed as certified by the Canadian Standards Association, Guide No. 69-11.19, Class 1432, File 18328.

#### Underwriters Laboratories listing

All grounding bars manufactured comply with Underwriters Laboratories standards and are listed under Guide No. DHJR, File E31424, Volume W, Section 17.

All circuit breakers 10 A and larger comply with the Underwriters Laboratories "Standard for Branch Circuit and Service Circuit-Breakers" UL 489; Guide No. 60 10.2 File E31424, and "Requirements for Wire Connectors and Soldering Lugs," UL 486B, Guide No. 461 10-C File E7830.

All Eaton breakers where marked, are suitable for use with 60/75  $^{\circ}$  rated wire, unless otherwise specified.

All devices comply with the 22–10 kAIC UL series connected components File DKSY2 of the Recognized Components Index.

#### **Product selection**







Table 26. Plug-in OEM loadcentre interior assemblies

Ampere rating	1-inch spaces	½-inch spaces	Main terminal size (per phase)	Package quantity	Catalogue number
125	4	8	(1) 2/0-#14 AWG Cu/AI	20	48INT125B
125	8	16	(1) 2/0-#14 AWG Cu/AI	20	816INT125B
125	12	24	(1) 2/0-#14 AWG Cu/AI	20	1224INT125B
125	16	24	(1) 2/0-#14 AWG Cu/AI	20	1624INT125B
125	20	24	(1) 2/0-#14 AWG Cu/AI	10	2024INT125B
125	24	24	(1) 2/0-#14 AWG Cu/Al	10	2424INT125B

## **Dimensions**




Figure 7. 48INT125B




Figure 8. 816INT125B




Figure 9. 1224INT125B




Figure 10. 1624INT125B




Figure 11. 2024INT125B




Figure 12. 2424INT125B

## Type CH plug-in loadcentres

#### **Product description**

Loadcentres feature factory installed main lugs or main circuit breakers. The CH interiors are manufactured of formed, silver flash plated copper. Eaton also supplies a full line of Type CH branch circuit breakers and accessories for these loadcentres.

### **Product application**

Designed for the protection and distribution of single and multidwelling residential and light commercial loads to 120/240 volts AC, such as lighting, heating, appliance and small motor branch circuits. All main circuit breaker combination loadcentres are CSA listed for use as service entrance equipment.

#### **Ratings**

Single-phase, three-wire, 120/240 volts AC. Mains through 200 A. Available with up to 120 branch circuits. Main breakers on 100 and 200 A panels are rated at 35,000 AIC.

## Metal enclosure specifications

Enclosures are made of 16 gauge galvanized sheet steel powder coated sandalwood beige. The galvanized coating provides corrosion protection. Trims are similarly scratch-resistant powder coated a sandalwood beige colour to match the tub. A combination surface/flush cover with integral door is supplied.

All plug-in loadcentres are CSA listed to file LL98266.

#### Warranty

Limited lifetime.

## Type CH plug-on neutral loadcentre features and benefits

Ample cable entry knockouts -

- Sidewall, endwall, and backplane locations
- Standard sizing for service entrance and branch circuit cabling

Commercial grade main circuit breaker

- 35 kAIC series rated main circuit breaker
- · Highest in the industry

Attractive sandalwood finish


- Esthetically appealing, scratch-resistant powder coating
- · Both tub and trim are painted

Silver flash plated copper bus

· Provides superior connectivity

Patented stab design

- Unique design provides a tight connection to the bus
- Prevents the misapplication of non-approved branch circuit breakers



Large service entrance section

- · Straight-in wiring saves labour and material
- Large cable bending space

Inboard neutral connections

- Provides direct neutral connection for plug-on style ground fault and arc fault circuit breakers
- Ample additional 2/0 lugs provided no kits necessary

Steel backpan

- Reliable breaker mounting
- One-piece design provides superior stability

Drywall marking on enclosure

 Indicates proper mounting depth for flush mounting applications

Single keyhole mounting

One keyhole at the top and bottom provides easier mounting and leveling

# Type CH plug-in loadcentres

## Combination and non-combination single-phase

Three-wire 120/240 Vac plug-on neutral style combination service entrance Type 1 (indoor)

Table 27. Type CH Main circuit breaker plug-on neutral indoor Type 1 loadcentres

Maximum	Main	May no		Type of main	Dimensions in inches (mm)			Wire size	
ampere rating	breaker rating	ker 3/4-inch Co	nch Cover	of main circuit breaker	н	w	D	range for main Cu/Al	Catalogue number
100	100	24	Flush/surface	CSR	29.13 (739.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM124
100	100	32	Flush/surface	CSR	34.13 (866.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM132
125	125	32	Flush/surface	CSR	34.13 (866.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM132Z
100	100	42	Flush/surface	CSR	37.00 (939.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM142
125	125	42	Flush/surface	CSR	37.00 (939.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM142Z
200	200	42	Flush/surface	CSR	37.00 (939.8)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM242
200	200	60	Flush/surface	CSR	45.00 (1143.0)	14.3 (363.2)	3.9 (99.06)	#2-300 kcmil	CCHPM260

Three-wire 120/240 Vac plug-on neutral style non-combination service entrance Type 1 (indoor)

Table 28. Type CH main lug only plug-on neutral indoor Type 1 loadcentres

Maximum	Max. no. 3/4-inch	0	Dimensions in	Dimensions in inches (mm)			0-4-1
ampere rating	spaces	Cover style	Н	w	D	range for main Cu/Al	Catalogue number
125	24	Flush/surface	29.13 (739.8)	14.3(363.2)	3.9 (99.06)	#2-300 kcmil	CCHPL124
225	32	Flush/surface	34.13 (866.8)	14.3(363.2)	3.9 (93.06)	#2-300 kcmil	CCHPL232

Three-wire 120/240 Vac standard neutral non-combination Type 3R (outdoor/raintight) ab







RCCHL102

Table 29. Type CH main lug only standard neutral outdoor/raintight Type 3R loadcentres a

Maximum ampere	Catalogue	Max. no. 3/4-inch	Max. no. 3/8-inch	Enclosure	Dimensions i	in inches (mm)		Wire size — range for
rating	number	spaces	spaces	style	Н	W	D	main CU/AL
100	RCCHL102	2	4	Indoor/outdoor Type 3R ac	12.00 (304.8)	6.88 (174.62)	4.38 (111.13)	#14-1/0
125	CH6L125R	6	12	Indoor/outdoor Type 3R	12.00 (304.8)	6.88 (174.62)	4.38 (111.13)	#14-1/0

a Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See  ${f page}$  15 for selection.

b Does not accept plug-on neutral style of arc fault and ground fault circuit breakers. Uses standard type arc fault and ground fault circuit breakers.

c Enclosure assembly incorporates a swing out locking hasp for the cover.

## Type CH single, multi-pole, and twin

## Type CH plug-in circuit breakers a

- 10,000 A interrupting capacity at 120/240 Vac
- · Flag trip models provide visual indication of trip

## Product selection

Table 30. Single- and multi-pole plug-in breakers

	Catalogue Number		
Wire size range (Cu/AL 60 °C or 75 °C) (AWG)	Single-pole, 120/240 Vac Flag trip indication 10 per shelf carton	Two-pole, 120/240 Vac Flag trip indication 5 per shelf carton	Three-pole, 240 Vac Standard 5 per shelf carton
(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	_	_	_
(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHF115	CHF215	СН315 h
(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHF120	CHF220	CH320 h
(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHF125	CHF225	CH325 h
(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHF130	CHF230	СН330 h
#14-2 b, #14-6 d	CHF135	CHF235	СН335 h
#10-1/0 e, #14-2 f, #3-0 g	CHF140	CHF240	СН340 h
#10-1/0 e, #14-2 f, #3-0 g	CHF145	CHF245	СН345 h
#10-1/0 e, #14-2 f, #3-0 g	CHF150	CHF250	СН350 h
#10-1/0 e, #14-2 f, #3-0 g	CH160	CH260	СН360 h
#10-1/0 e, #14-2 f, #3-0 g	CH170	CH270	СН370 h
#10-1/0 e, #14-2 f, #3-0 g	_	CH280	CH380
#10-1/0 e, #14-2 f, #3-0 g	_	CH290	CH390
#10-1/0 e, #14-2 f, #3-0 g	_	_	CH3100
#10-1/0 e, #14-2 f, #3-0 g	_	_	_
#10-1/0 e, #14-2 f, #3-0 g	_	_	_
			Requires three ¾-inch (19.1 mm) spaces
	(Cu/AL 60 °C or 75 °C) (AWG)  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  #10-1/0 e, #14-6 d  #10-1/0 e, #14-2 f, #3-0 g  #10-1/0 e, #14-2 f, #3-0 g	Wire size range (Cu/AL 60 °C or 75 °C) (AWG)  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-8 b, (2) #14-10 bc, (1) #14-6 d  (1) #14-2 b, #14-6 d  (2) #14-10 bc, (1) #14-6 d  (3) #14-2 b, #14-2 f, #3-0 g  (4) #10-1/0 c, #14-2 f, #3-0 g  (4) #10-1/0 c, #14-2 f, #3-0 g  (5) #10-1/0 c, #14-2 f, #3-0 g  (6) #10-1/0 c, #14-2 f, #3-0 g  (7) #10-1/0 c, #14-2 f, #3-0 g  (8) #10-1/0 c, #14-2 f, #3-0 g  (9) #10-1/0 c, #14-2 f, #3-0 g  (1) #10-1/0 c, #14-2 f, #3-0 g  (2) #10-1/0 c, #14-2 f, #3-0 g  (3) #10-1/0 c, #14-2 f, #3-0 g  (4) #10-1/0 c, #14-2 f, #3-0 g	Wire size range (Cu/AL 60 °C or 75 °C) (AWG)         Single-pole, 120/240 Vac Flag trip indication 10 per shelf carton         Two-pole, 120/240 Vac Flag trip indication 5 per shelf carton           (1) #14−8 b, (2) #14−10 bc, (1) #14−6 d         —         —           (1) #14−8 b, (2) #14−10 bc, (1) #14−6 d         CHF115         CHF215           (1) #14−8 b, (2) #14−10 bc, (1) #14−6 d         CHF120         CHF220           (1) #14−8 b, (2) #14−10 bc, (1) #14−6 d         CHF125         CHF225           (1) #14−8 b, (2) #14−10 bc, (1) #14−6 d         CHF130         CHF230           #14−2 b, #14−6 d         CHF135         CHF235           #10−1/0 e, #14−2 f, #3−0 g         CHF140         CHF240           #10−1/0 e, #14−2 f, #3−0 g         CHF145         CHF245           #10−1/0 e, #14−2 f, #3−0 g         CHF150         CHF250           #10−1/0 e, #14−2 f, #3−0 g         CH160         CH260           #10−1/0 e, #14−2 f, #3−0 g         CH170         CH270           #10−1/0 e, #14−2 f, #3−0 g         —         CH290           #10−1/0 e, #14−2 f, #3−0 g         —         CH290           #10−1/0 e, #14−2 f, #3−0 g         —         —

a Not for use in Type BR loadcentres

## Type CHTwin Circuit Breakers abc

- 10,000 A interrupting capacity at 120/240 Vac
- Provides 2 single-pole circuits in one ¾-inch space

Table 31. Twin plug-in circuit breakers

		Catalogue number
Ampere rating	Wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Single-pole, 120/240 Vac 10 per shelf carton
15-15	#14-8	CHT1515
15-20	#14-8	CHT1520
20-20	#14-8	CHT2020
		Requires one ¾-inch (19.1 mm) space

a Switching duty rated.

b For single- and two-pole breakers.

c Solid and stranded wire can be used together.

d For three-pole breakers.

e Single-pole 60-70 A, two-pole 80-125 A, three-pole 40-100 A.

f Single-pole 40-50 A, two-pole 40-70 A.

g Two-pole 150 A.

h HACR rated.

b HACR rated.

c Not for use in Type BR loadcentres i.e. CPM or CPL prefixed catalogue numbers.

# Plug-in circuit breakers for CH

# Type CHP commercial

Type CHP commercial circuit breakers a

- 10,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac
- Three-position trip breakers for commercial applications when On-Off and Trip position is required

Table 32. Commercial plug-in circuit breakers

Cata	logue	number
------	-------	--------

Ampere rating	Wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Single-pole 120/240 Vac 10 per shelf carton	Two-pole 120/240 Vac 5 per shelf carton	Three-pole 240 Vac 5 per shelf carton
10	(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHP110	_	CHP310
15	(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	<b>CHP115</b> gh	CHP215 h	CHP315 h
20	(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHP120 gh	CHP220 h	CHP320 h
25	(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHP125 h	CHP225 h	CHP325 h
30	(1) #14-8 b, (2) #14-10 bc, (1) #14-6 d	CHP130 h	CHP230 h	СНР330 h
35	#14-2 b, #14-6 d	CHP135 h	CHP235 h	СНР335 h
40	#10-1/0 e, #14-2 f	CHP140 h	CHP240 h	СНР340 h
45	#10-1/0 e, #14-2 f	CHP145 h	CHP245 h	СНР345 h
50	#10-1/0 e, #14-2 f	CHP150 h	CHP250 h	CHP350 h
60	#10-1/0 e, #14-2 f	— h	CHP260 h	СНР360 h
70	#10-1/0 e, #14-2 f	_	CHP270	CHP370
80	#10-1/0 e, #14-2 f	_	CHP280	_
90	#10-1/0 e, #14-2 f		CHP290	_
100	#10-1/0 e, #14-2 f	_	CHP2100	CHP3100
110	#10-1/0 e, #14-2 f	_	_	_
125	#10-1/0 e, #14-2 f	_	CHP2125	_
		Requires one ¾-inch (19.1 mm) space	Requires two ¾-inch (19.1 mm) spaces	Requires three ¾-inch (19.1 mm) spaces

a Not for use in Type BR loadcentres

b For single- and two-pole breakers.

 $<sup>\</sup>boldsymbol{c}$  Solid and stranded wire can be used together.

d For three-pole breakers.

e Single-pole 60-70 A, two-pole 80-125 A, three-pole 40-100 A.

f Single-pole 40-50 A, two-pole 40-70 A.

g Switching duty rated.

h HACR rated.

## Type CH arc fault circuit interrupter

Type CH arc fault circuit interrupter circuit breakers a

- 10,000 A interrupting capacity at 120 Vac, and 120/240 Vac
- Plug-on neutral style for plug-on neutral type CH loadcentres


A combination type arc fault circuit interrupter is a device intended to mitigate series and parallel arcing faults in the complete circuit, including connected cords. Parallel arcing faults can occur from line to neutral or line to ground. These arcing faults are in parallel with the load and produce the most energy of all arcing faults.

Table 33. Single- and two-pole plug-in FIRE-GUARD AFCI circuit breakers

			Catalogue number	
Ampere rating	Wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Configuration	Single-pole, 120/240 Vac 10 per shelf carton 10 kAIC	Two-pole, 120/240 Vac 5 per shelf carton 10 kAIC <sup>b</sup>
15	#14-4	Pigtail	CHFCAF115	CH215CAF
15	#14-4	Plug-on neutral c	CHFCAF115PN	<u> </u>
20	#14-4	Pigtail	CHFCAF120	CH220CAF
20	#14-4	Plug-on neutral c	CHFCAF120PN	<u> </u>
			Requires one ¾-inch (19.1 mm) space	Requires two ¾-inch (19.1 mm) spaces

a Not for use in Type BR loadcentres

c Only for use in the Type CH plug-on neutral style of combination and non-combination loadcentres.



120/240 Vac
Source
N A B
Line B
Line

Figure 13. Single-pole, single 120 V load application sourced by 120/240 Vac

Figure 14. Two-pole, 240 V load application sourced by 120/240 Vac



Type CH single-pole AFCI circuit breaker



Type CH single-pole dual-purpose AFGF breaker

Table 34. Single-pole plug-in dual purpose AF/GF circuit breakers

Ampere rating	Wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Configuration	Catalogue number Single-pole 120/240 Vac 10 per shelf carton 10 kAIC	
15	#14-4	Pigtail	CHFAFGF115	
15	#14-4	Plug-on neutral a	CHFAFGF115PN	_
20	#14-4	Pigtail	CHFAFGF120	
20	#14-4	Plug-on neutral a	CHFAFGF120PN	_
	Combination AFCI and 5 mA people protection ground fault		Requires one ¾-inch (19.1 mm) space	

a Only for use in the Type CH plug-on neutral style of combination and non-combination loadcentres.

b Common trip refers to two-pole 240 V load application sourced by 120/240 Vac (see Figure 14).

## Plug-in circuit breakers for CH

## Type CH ground fault

Type CH ground fault circuit breakers a

- 10,000 A interrupting capacity at 120 Vac and 120/240 Vac
- 5 mA "people protection" or 30 mA equipment protectors
- Two-pole version features common trip

Table 35. (5 mA) single- and two-pole plug-in ground fault circuit breakers

		Catalogue number		
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Single-pole, 120 Vac Standard Pigtail 1 per shelf carton 10 kAIC	Single-pole, 120 Vac Plug-on neutral b 1 per shelf carton 10 kAIC	Two-pole 120/240 Vac Standard 1 per shelf carton 10 kAIC
15	#14–6 c	CHFGFT115	CHFGFT115PN <sup>b</sup>	CH215GFT
20	#14-6 c	CHFGFT120	CHFGFT120PN b	CH220GFT
25	#14-6 c	CHFGFT125	_	CH225GFT
30	#14-6 c	CHFGFT130	CHFGFT130PN b	CH230GFT
35	#14-6 c	_	_	CH235GFT
40	#14-6 c	_	_	CH240GFT
45	#14-6 c	_	_	CH245GFT
50	#14-6 c	_	_	CH250GFT
60	#14-6 c	_	_	CH260GFT
		Requires one ¾-inch (19.1 mm) space		Requires two ¾-inch (19.1 mm) spaces

a Not for use in Type BR loadcentres

Table 36. (30 mA) single- and two-pole plug-in ground fault circuit breaker equipment protectors

		Catalogue number	
Ampere rating	Wire size range Cu/AI 60 °C or 75 °C (AWG)	Single-pole, 120 Vac 1 per shelf carton 10 kAIC	Two-pole, 120/240 Vac 1 per shelf carton 10 kAIC
15	#14-6 a	CHFEP115	CH215EPD
20	#14-6 a	CHFEP120	CH220EPD
25	#14-6 a	CHFEP125	_
30	#14-6 a	CHFEP130	CH230EPD
40	#14-6 a	_	CH240EPD
50	#14-6 a	_	CH250EPD
60	#14-6 a	_	CH260EPD
		Requires one ¾-inch (19.1 mm) space	Requires two ¾-inch (19.1 mm) spaces

a 60 A breaker listed for 75 °C Cu wire only.

#### **Ground fault application**

Single-pole ground fault circuit breakers (Type CHGFIs) are designed for use in two-wire, 120 Vac circuits. **Figure 15** shows a typical wiring configuration. Two-pole ground fault circuit breakers (Type CHGFIs) are designed for use in three-wire, 120/240 Vac circuits, 120 Vac multi-wire circuits employing common, neutral and two-wire, 240 Vac circuits obtained from a 120/240 Vac source. **Figure 16** and **Figure 17** illustrate typical wiring configurations for 120/240 Vac multi-wire circuits. **Figure 18** depicts a 240 Vac, two-wire circuit. Note the "panel neutral" conductor connects to the neutral bar, even though the neutral is not included in the load circuit. This connection is necessary to supply a 120 Vac power source to the ground fault sensing circuit. The figures are shown with a 120/240 Vac, single-phase, three-wire power source, but are also applicable to a 120/208 Vac, three-phase, four-wire power supply. For all figures the electrical operation of the Type CHGFI is not affected by the equipment ground.



Type CH two-pole GFCI circuit breaker




Figure 15. Single-pole single 120 V duplex receptacle application




Figure 16. Two-pole 120 V multi-duplex receptacle application




Figure 17. Two-pole 120 V duplex receptacle application




Figure 18. Two-pole 240 V duplex receptacle application

b Only for use in the Type CH plug-on neutral style of combination and non-combination loadcentres.

c 60 A breaker listed for 75 °C Cu wire only.

# Plug-in loadcentre main circuit breakers for CH

# Type CSR

Type CSR loadcentre main circuit breaker kit

• 25,000 A interrupting capacity at 120/240 Vac



CSR2150N

# Product selection

# Table 37. Two-pole main circuit breakers for single-phase plug-in combination loadcentres

		Catalogue number	
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C	Two-pole, 120/240 Vac 1 per shelf carton 25 kAIC	
100	#2 AWG-300 kcmil	CSR2100N	
125	#2 AWG-300 kcmil	CSR2125N	
150	#2 AWG-300 kcmil	CSR2150N	
200	#2 AWG-300 kcmil	CSR2200N	

# Plug-in loadcentres and circuit breaker accessories for CH

## Type CH loadcentre and circuit breaker accessories

#### Table 38a. Field installation kits and parts for plug-in loadcentres and circuit breakers

Description	Ordering quantity <sup>a</sup>	Catalogue number
Bonding kit for bonding the neutral bus to the loadcenter	1	BONDKITP
Brown cover replacement latch—indoor loadcenters	1	LATCHPS
Retaining bracket for backfed main breaker—CH	1	CHPHD

## Table 38b. Legacy Field installation kits and parts for CH loadcentres and circuit breakers

Description	Ordering quantity <sup>a</sup>	Catalogue number
Handle tie for single-pole Type CH circuit breakers. Joins handles on breakers mounted adjacent to each other via a moulded plastic handle cover.	1	СННТ
Handle lockoff (escutcheon mounted). Single- or two-pole Type CH circuit breakers.	1	CHPL
Handle lockoff (escutcheon mounted). Single- or two-pole Type CHGFI circuit breakers.	1	CHPLGF
Handle lockoff (escutcheon mounted). Locks the handle of main circuit breaker type CSH in the OFF of ON position.	1	MCBPL
Handle lockdog (handle mounted). Single-pole Type CH circuit breakers. Secures handle in the ON or OFF position.	1	CHLO
Subfeed kit for 125 A loadcentres. Requires two 3/4-inch (19.1 mm) spaces.	1	CHSF2125
3/4-inch (19.1 mm) filler plate kit a	1	CHFP a
Door lock for 24–60 circuit 100 and 200 A (CH)	1	TDL b
Trim screw kit (CH)	1	LCCS c
Sandalwood plastic replacement door latch	1	CHRLS
Branch circuit numbering strip kit for CH	1	CHMS d
Electronic breaker lockoff (escutcheon mounted) for type CHFCAF and CHFAFGF		CHFAFGFLOFF

a Kit includes 25 pieces.

## **Definitions**

Handle ties: Devices used to join two similar independent single-pole circuit breakers to form a two-pole non-common trip breaker.

Handle lockoffs: Devices that use a padlock to lock a circuit breaker's handle in either the ON or OFF position.

Handle lockdogs: Devices used to secure a circuit breaker's handle in the ON or OFF position. They are not padlockable devices.

Escutcheon mounted: A semipermanent mounting to the face of the circuit breaker and secured by the loadcentre's deadfront cover.

Handle mounted: A mounting made directly to the handle of the circuit breaker by means of a set screw.

Screw mounted: A permanent mounting to the face of the circuit breaker by means of a non-removable screw.

b Comes with a set of keys.

c Kit includes 25 pieces.

d Kit includes 20 pieces.

## Combination Service Entrance (main circuit breaker) single- and three-phase aluminum bus

Single-phase 120/240 VacType 1 (indoor) loadcentres combination service entrance

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers



3CBM230

#### Product selection

Table 39. Single-phase, three-wire 120/240 Vac aluminum bus loadcentres

Maximum				Dimensions i		Catalogue			
ampere rating		Cover style	Н	w	D	D Wire size range D for main Cu/Al			
125	100	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	CBM118 a
125	100	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	<b>CBM130</b> a
125	100	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	CBM142 a
225	200	18	36	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#4-4/0	CBM218 b
225	200	30	60	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#4-4/0	СВМ230 ь

a BAB2100 main circuit breaker factory installed.

## Three-phase Combination service entrance 240 Vac Type 1 (indoor) loadcentres

- CSA certified only (not UL spproved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers

Table 40. Three-phase, four-wire 240 Vac maximum aluminum bus loadcentres

Maximum	Main	Max. no.	Max. no.	•	Dimensions in inches (mm)				
ampere rating	breaker rating	1-inch spaces	1/2-inch spaces	Cover style	н	w	D	Wire size range for main Cu/Al	Catalogue number
125	100	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 Al	3CBM118 a
125	100	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 Al	3CBM130 a
125	100	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 Al	3CBM142 a
225	200	18	36	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#4-4/0	3CBM218 b
225	200	30	60	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#4-4/0	3CBM230 b

a BAB3100H main circuit breaker factory installed.

b ED2200 main circuit breaker factory installed.

b ED3200 main circuit breaker factory installed.

## Type CBM/CBL bolt-on loadcentres

## Combination (main circuit breaker) single- and three-phase copper bus

Single-phase 120/240 VacType 1 (indoor) loadcentres combination service entrance

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers

Table 41. Single-phase, three-wire 120/240 Vac copper bus loadcentres

Maximum	Main	Max. no.	Max. no.	Cover	Dimensions in inches (mm)				Catalanus
ampere rating	breaker rating	1-inch spaces	1/2-inch spaces	style	н	w	D	Wire size range for main Cu/Al	Catalogue number
125	100	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	CBM118CU a
125	100	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	CBM130CU a
125	100	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	CBM142CU a
225	200	18	36	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#4-4/0	CBM218CU b
225	200	30	60	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#4-4/0	CBM230CU b

a BAB2100 main circuit breaker factory installed.

#### Three-phase combination service entrance 240 Vac Type 1 (indoor) loadcentres

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGFT circuit breakers as branch circuit breakers

Table 42. Three-phase, four-wire 240 Vac maximum copper bus loadcentres

Maximum	Main	Max. no.	Max. no. 1/2-inch	Cover	Dimensions in inches (mm)				0-4-1
ampere rating	breaker rating	1-inch spaces	spaces	style	н	w	D	── Wire size range for main Cu/Al	Catalogue number
125	100	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	3CBM118CU a
125	100	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	3CBM130CU a
125	100	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#8-#1 Cu / #8-1/0 AI	3CBM142CU a
225	200	30	60	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#4-4/0	3CBM230CU b

a BAB3100H main circuit breaker factory installed.

b ED2200 main circuit breaker factory installed.

b ED3200 main circuit breaker factory installed.

## Non-combination (main lug only) single- and three-phase aluminum bus

Single-phase 120/240 Vac Type 1 (indoor) loadcentres

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers



CBL130

Table 43. ingle-phase, three-wire 120/240 Vac aluminum bus loadcentres

Maximum	Max. no.	Max. no. 1/2-inch spaces	Cover style	Dimensions in inches (mm)			Wire size range	Catalogue
ampere rating	1-inch spaces			Н	w	D	for main Cu/Al	number
125	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL118
125	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL130
125	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL142
225	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL218
225	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL230
225	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL242

## Three-phase 240 VacType 1 (indoor) loadcentres

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers

Table 44. Three-phase, four-wire 240 Vac aluminum bus loadcentres

Maximum	Max. no.	Max. no. 1/2-inch spaces	Cover style	Dimensions in	inches (mm)	Wire size range	0-4-1	
ampere rating	1-inch spaces			н	w	D	for main Cu/Al	Catalogue number
125	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL118
125	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL130
125	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL142
225	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL218
225	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL230
225	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL242

## Type CBM/CBL bolt-on loadcentres

## Non-combination (main lug only) single- and three-phase copper bus

Single-phase 120/240 Vac Type 1 (indoor) loadcentres

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers

Table 45. Single-phase, three-wire 120/240 Vac copper bus loadcentres

Maximum	Max. no.	Max. no.	Cover style	Dimensions in inches (mm)				
ampere 1-inch rating spaces		1/2-inches spaces		н	w	D	──── Wire size range for main Cu/Al	Catalogue number
125	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL118CU
125	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL130CU
125	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL142CU
225	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL218CU
225	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL230CU
225	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	CBL242CU

## Three-phase 240 Vac Type 1 (indoor) loadcentres

- CSA certified only (not UL approved)
- Utilize Type BAB, QBHW, QBA, DNBA, or QBGF circuit breakers as branch circuit breakers

Table 46. Three-phase, four-wire 240 Vac copper bus loadcentres

Maximum Max. no.		Max. no.		Dimensions in inches (mm)				0-4-1
ampere 1-inch rating spaces	1/2-inches spaces	Cover style	Н	w	D	Wire size range for main Cu/Al	Catalogue number	
125	18	36	Flush/surface	27.00 (685.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL118CU
125	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL130CU
125	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL142CU
225	30	60	Flush/surface	34.13 (866.8)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL230CU
225	42	84	Flush/surface	39.00 (990.6)	14.25 (361.9)	3.75 (95.3)	#6-300 MCM	3CBL242CU

**BAB3100H** 

QBHW3090

**QBHW3100** 

Requires three 1-inch (25.4 mm) spaces

#### Type BAB and QBHW single- and multi-pole

Type BAB and QBHW

• 10,000/22,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac

Product selection

100

125

Table 47. Single- and multi-pole bolt-on circuit breakers

Catalogue number Single-pole, 120/240 Vac Two-pole, 120/240 Vac Three-pole, 120/240 Vac Wire size range (Cu/Al 60 °C or 75 °C) (AWG) Ampere rating 10 kAIC 10 kAIC 10 kAIC 22 kAIC 22 kAIC 22 kAIC 10 #14-4 **BAB1010** #14-4 15 **BAB1015 QBHW1015 BAB2015 QBHW2015 BAB3015H QBHW3015** 20 #14-4 **BAB1020 QBHW1020 BAB2020 QBHW2020 BAB3020H QBHW3020** 25 #14-4 BAB1025 **QBHW1030 QBHW2030 BAB3030H QBHW3030** 30 #14-4 BAB1030 **BAB2030** 40 #14-4 **BAB1040 QBHW1040 BAB2040 QBHW2040 BAB3040H QBHW3040** 50 #14-4 **QBHW3050 BAB1050** QBHW1050 **BAB2050 QBHW2050 BAB3050H** 60 #8-1 Cu, #8-1/0 AI **BAB1060 QBHW1060 BAB2060 QBHW2060 BAB3060H** QBHW3060 70 #8-1 Cu, #8-1/0 AI **BAB1070** QBHW1070 BAB2070 **QBHW2070 BAB3070H** QBHW3070 90 **BAB3090H** 

**BAB2090** 

**BAB2100** 

**BAB2125** 

**QBHW2090** 

**QBHW2100** 

**QBHW2125** 

Requires two 1-inch (25.4 mm) spaces

## Type BAB high intensity discharge (HID) rated

#8-1 Cu, #8-1/0 AI

#8-1 Cu, #8-1/0 AI

#8-1 Cu, #8-1/0 AI

• 10,000 A interrupting capacity at 120 Vac, 120/240 Vac, and 240 Vac

Requires one 1-inch (25.4 mm) space

Table 48. Single-pole HID rated bolt-on circuit breakers

Catalogue number				
/ac				
mm) space				

Table 49. Single-pole bolt-on fire alarm breakers

		Catalogue number				
Ampere rating	Configuration	Single-pole, 120/240 Vac 10 per shelf carton 10 kAIC				
15	Branch fire alarm	BABF1015				
20	Branch fire alarm	BABF1020				
	Compact body breaker	Requires one 1-inch (25.4 mm) space				

## **Bolt-on circuit breakers for CBM/CBL**

## Type QBA arc fault circuit interrupter and DNBA duplex

Type QBA Arc fault circuit interrupter circuit breakers

• 10,000/22,000 A interrupting capacity at 120 Vac 120/240 Vac, and 240 Vac

## Table 50. Single- and two-pole bolt-on FIRE-GUARD AFCI circuit breakers

		Catalogue number		
		Single-pole 120/240 Vac	Wire size range	
Ampere rating	Configuration	10 kAIC	22 kAIC	———— (Cu/AI 60 °C or 75 °C) (AWG)
15	Combination	QB1015CAF	QBH1015CAF	#14-4
15	Dual With GFCI 5mA	QB1015AFGF	QBH1015AFGF	#14-4
20	Combination	QB1020CAF	QBH1020CAF	#14-4
20	Dual With GFCI 5mA	QB1020AFGF	QBH1020AFGF	#14-4
		Requires one 1-inch (25.4 mm) space	Requires one 1-inch (25.4 mm) space	

## Type DNBA duplex circuit breakers

- 10,000 A interrupting capacity at 120/240 Vac
- Provides 2 single-pole circuits in one 1-inch space

Table 51. Twin plug-in circuit breakers

	Wire cize range	Catalogue number				
Ampere rating	Wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Single-pole, 120/240 Vac 10 per shelf carton				
15–15	#14-4	DNBA1515				
20-20	#14-4	DNBA2020				
30-30	#14-4	DNBA3030				
		Requires one 1-inch (25.4 mm) space				




Figure 19. Single-pole, single 120 V load application sourced by 120/240 Vac

## Type QBGF and QBGFEP ground fault

## Type QBGF and QBGFEP ground fault circuit breakers

- 10,000/22,000 A interrupting capacity at 120 Vac and 120/240 Vac
- 5 mA "people protection" or 30 mA equipment protectors
- Two-pole version features common trip

## Table 52. (5 mA) single- and two-pole bolt-on ground fault circuit breakers

		Catalogue number				
Ampere rating	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Single-pole, 120 Vac 1 per shelf carton 10 kAIC	Two-pole, 120/240 Vac 1 per shelf carton 10 kAIC			
15	#14-10 Cu, #12-10 Al	QB1015GF	QBGFT2015			
20	#14-10 Cu, #12-10 Al	QB1020GF	QBGFT2020			
30	#10 Cu, #8 AI	QB1030GF	QBGFT2030			
40	#8 Cu, #8-6 AI	QBGFT1040	QBGFT2040			
50	#8-6 Cu, #6-4 AI	_	QBGFT2050			
		Requires one 1-inch (25.4 mm) space	Requires two 1-inch (25.4 mm) spaces			

## Table 53. (30 mA) single- and two-pole bolt-on ground fault circuit breaker equipment protectors

	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Catalogue number	Catalogue number						
Ampere rating		Single-pole, 120 Vac 1 per shelf carton		Two-pole, 120/240 Vac 1 per shelf carton					
		10 kAIC	22 kAIC	10 kAIC	22 kAIC				
15	#14-4	QB1015EP	QBH1015EP	QBGFEP2015	QBHGFEP2015				
20	#14-4	QB1020EP	QBH1020EP	QBGFEP2020	QBHGFEP2020				
25	#14-4	QB1025EP	QBH1025EP	QBGFEP2025	QBHGFEP2025				
30	#14-4	QB1030EP	QBH1030EP	QBGFEP2030	QBHGFEP2030				
		Requires one 1-inch (25.4 mm) space	Requires one 1-inch (25.4 mm) space	Requires two 1-inch (25.4 mm) spaces	Requires two 1-inch (25.4 mm) spaces				

## **Bolt-on loadcentre and circuit breaker accessories**

#### **Bolt-on accessories**

Table 54. Field installation kits and parts for bolt-on loadcentres and circuit breakers

Description	Ordering quantity	Catalogue number
Handle lockoff single-pole of Type DNBA duplex circuit breakers (package of 10)	1	BRDL1-10
Handle lockoff Type BQL circuit breakers	1	BQL-10
Handle lockoff Type BAB and QBHW circuit breakers	1	QL123PL
Handle lockdog single-pole Type BAB and QBHW circuit breakers	1	QL1NPL
Handle lockdog two- and three-pole Type BAB and QBHW circuit breakers	1	QL23NPL
Filler plates 1-inch space (package of 24)	1	BRFP
Subfeed lug 100 A (for main lug panel style)	1	CBSF100
Subfeed lug 225 A (for main lug panel style)	1	CBSF225
Subfeed lug kit 100 A three-phase (for main lug panel style)	1	3CBSF100
Subfeed lug kit 225 A three-phase (for main lug panel style)	1	3CBSF225
Circuit breaker directory card 1–42 (package of 50)	1	DIRCARD42
Circuit breaker directory sleeve (package of 25)	1	DIRSLEEVE
Loadcentre door lock	1	TDL
Isolated ground kit	1	ISGRD

## **Definitions**

Handle lockoffs: Devices that use a padlock to lock a circuit breaker's handle in either the ON or OFF position.

Handle lockdogs: Devices used to secure a circuit breaker's handle in the ON or OFF position. They are not padlockable devices.

#### Manual transfer switches/generator panels

#### **Product description**

A transfer switch panel is a device that is mounted next to or incorporated within the loadcentre (distribution panel) in the home or small business. The transfer switch panel is used in conjunction with an emergency generator (usually supplied by others) and serves the purpose of turning selected circuits on and off during a power outage. The transfer switch panel allows the owner to start up a generator and then restore power to critical circuits when utility power is not available.

The owner designates which circuits are critical such as their refrigerator, furnace, and certain lighting loads. Sometimes called emergency power panels, emergency generator panels, gen. panels, transfer switches or emergency panels; transfer switch panels provide the homeowner or small business owner with a safe and easy way to continue using essential electrical loads when utility power is not available.

#### **Application description**

Transfer switch panels are most often used in residential, agricultural and light commercial applications. Comfort and safety are key concerns of many homeowners who are dependent on an uninterrupted supply of electricity.

The increase in our dependence on power is due in part to the popularity of home business and in-home care. In addition, various rural and urban regions in North America experience periodic power outages due to extreme weather conditions such as ice and snowstorms, heat waves, tornadoes or hurricanes. Regions such as Pacific, Atlantic, and Central are the strongest markets for portable generators and transfer switch panels.

#### Features, functions, and benefits

Eaton offers two unique manual transfer switch emergency power solutions.

- · Manual transfer switches or a generator sub-panel
- Combination service entrance loadcentre with generator sub-panel

## **IMPORTANT**

BEFORE INSTALLATION, CONSULT APPROPRIATE ELECTRICAL CODES. INSTALLATION INFORMATION IS INCLUDED IN THE CARTON.

#### Manual transfer switches/generator panels

- · Main utility and emergency (generator) breaker factory installed
- · Available in 30 and 60 A design
- Utility breaker and generator breakers are mechanically interlocked to protect equipment and personnel by preventing dangerous dual-source feeding
- Critical loads permanently connected to allow for quick and convenient switching from utility power to stand-by generator power
- Designed for switched neutral applications. Can be reconfigured in field for non-switched neutral applications
- Sturdy and reliable 125 A rated aluminum bus design
- Type BR/DNPL branch breakers sold separately
- · Ideal for new and retrofit installations
- · EEMAC 1 indoor enclosure design
- · Standards and certifications
- · CSA approved

#### **Product specifications**

- 10,000 AIC rating
- · Switching devices must be circuit breakers
- Transfer switch panel must be supplied with neutral and ground

# Combination service entrance loadcentre generator panel CBRPM236GEN

- Single enclosure (EEMAC 1) to house both loadcentre and generator breakers
- · Factory installed main breakers
- · Available in 200 A designs
- Utility and emergency transfer switch breaker factory installed
- Utility breaker and generator breakers are mechanically interlocked to protect equipment and personnel by preventing dangerous dual-source feeding
- Critical loads permanently connected to allow for quick and convenient switching from utility power to stand-by generator power
- Designed for switched neutral applications. Can be reconfigured in field for non-switched neutral applications
- · Type BR/DNPL branch breakers sold separately
- · Ideal for new and retrofit installations
- EEMAC 1 indoor enclosure design

#### Standards and certifications

· CSA approved

#### **Product specifications**

- 25,000 AIC rating for CBRPM236GEN
- · Switching devices must be circuit breakers
- Transfer switch panel must be supplied with neutral and ground

## Manual transfer switches/generator panels

#### **Product selection**

Table 55. Manual transfer switches/generator panels

Bus rating (A)	Generator breaker (A)	Switched neutral	Enclosure rating	Max. total branch circuits (1-inch/½-inch)	Inlet receptacle type	Height branch circuits in inches (mm)	Width in inches (mm)	Depth in inches (mm)	Catalogue number
125	30	Yes	EEMAC 1	6/12	_	16.75 (425.5)	14.38 (365.1)	3.88 (98.4)	CBRPL112G3
125	60	Yes	EEMAC 1	6/12	_	16.75 (425.5)	14.38 (365.1)	3.88 (98.4)	CBRPL112G6
125	60	Yes	EEMAC 1	14/28	_	21.00 (533.4)	14.38 (365.1)	3.88 (98.4)	CBRPL120G6
125	60	Yes	EEMAC 1	24/48	_	29.13 (739.8)	14.38 (365.1)	3.88 (98.4)	CBRPL130G6

Table 56. Combination service entrance loadcentre generator panel

Bus rating (A)	Loadcentre main breaker (A)	Max. total branch circuits (1-inch/½-inch)	Generator breaker (A)	Switched neutral	generator branch circuits	Height in inches (mm)	Width in inches (mm)	Depth in inches (mm)	Catalogue number
200	200	36/72	60	Yes	6/12	49.00 (1244.6)	14.38 (365.1)	3.88 (98.4)	CBRPM236GEN




Figure 20. Typical installation diagram

#### Notes:

Combination service entrance loadcentre generator panels come complete with an integrated emergency generator panel.

Combination service entrance loadcentre generator panels come complete with factory installed utility feeder breaker for emergency generator panel section.

\* Not Included

# Single-phase, three-wire 120/240 Vac ground fault circuit interrupter spa panels

- · Factory assembled, prewired, tested, and ready to install
- Two-pole 5 mA "people protection" Type CH ground fault circuit interrupter circuit breaker
- Two additional one-pole circuits available
- Test button provides a means of confirming proper GFCI circuit breaker operation
- · 10,000 A interrupting capacity
- 120/240 Vac single-phase, three-wire
- · Pre-installed neutral and ground bars
- Type 3R enclosure good for indoor or outdoor mounting
- · Interior deadfront provides protection from energized parts
- · Padlockable cover provides added security and safety
- Audible alarm option field installable
- · Can be used as a disconnect to turn the spa pump on and off
- Main lug connections will accommodate a single #14–1/0 AWG conductor a



## Product description

CEC Rule 68-086 (1) and (6) requires that a ground fault circuit interrupter, of a Class A Type, be installed not closer than 3 m (10 ft) to a pool or spa water. In cases where a spa is installed some distance from your main loadcentre it is often more convenient to locate this protection device in a small panel closer to the spa. Excessive cable lengths required to connect directly back to a protection device in your main loadcentre may be more susceptible to insulation breakage and result in nuisance tripping of the breaker. The reduced distance the owner must travel to reset a tripped circuit breaker in a localized spa panel may also be an excellent selling point for the owner.

#### Product selection

Table 57. Two-pole plug-in Type 3R spa panels


Breaker amperage (A)	Breaker type	Enclosure style	Audible alarm	Height in inches (mm)	Width in inches (mm)	Depth in inches (mm)	Catalogue number
30	СН	Indoor/outdoor Type 3R a	N	12.00 (304.8)	6.88 (174.6)	4.50 (114.3)	CH30SPAST
40	СН	Indoor/outdoor Type 3R a	N	12.00 (304.8)	6.88 (174.6)	4.50 (114.3)	CH40SPAST
50	СН	Indoor/outdoor Type 3R a	N	12.00 (304.8)	6.88 (174.6)	4.50 (114.3)	CH50SPAST
60	СН	Indoor/outdoor Type 3R a	N	12.00 (304.8)	6.88 (174.6)	4.50 (114.3)	CH60SPAST

 $a \ {\hbox{Outdoor loadcentres accommodate Type DS conduit hubs. Hubs not included. See} \ \textbf{page 15} \ for \ selection.$ 

#### Table 58. Spa panel accessories

Description	Catalogue number
Field installable audible alarm kit (breaker and panel not included)	CHSPALARM

**Note:** CEC Rule 68-086 (1) and (6) requires that a ground fault circuit interrupter, of a Class A type, be installed not closer than 3 m (10 ft) to a pool or spa water.



Check national and local codes for compliance.

a Refer to page 34 for Type CH ground fault circuit breaker accepted load conductor sizes.

#### Surge suppression products

#### Stage 1 and Stage 1 Type 2

#### Residential surge suppression products

- Stage 1 surge protection as well as Type 1 and Type 2 offering
- Convenient in-panel mount unit for Type BR loadcentres
- Knockout mount or surface mount CHSP design. DIN mount adapter for Type 1
- Limited lifetime warranty on CHSPT2ULTRA
- Dovetail clip together cable surge accessories for CHSPT2 design
- · Flush mount kit for CHSPT2 design knockout mounting
- Type 2 surge suppression product designed to meet CSA C22.2 No.269-2 and UL 1449 3rd edition standard, cULus Listed No. N 024005





#### Product description

Today's homes are filled with increasing quantities of devices containing sensitive electronic components. These devices can easily be damaged by common power surges also some times called line transients, spikes, or voltage impulses. Lighting strikes, utility grid switching, other users on the powerline, and internal surges from air conditioners and powers tools are the most common sources these damaging line transients. To protect your investment it is recommended that a surge suppression device be installed. Surge protection can be broken into two stages. Stage 1 protection is primary protection for your service entrance. This protection is typically installed inside or adjacent to a home's service entrance distribution panel. Stage 2 protection is secondary protection or protection at the point of use. For proper surge protection both a stage 1 and stage 2 device must be installed. Eaton offers surge products to provide stage 1 protection to your sensitive equipment as well as both Type 1 and Type 2 surge devices that meet the latest CSA C22.2 No. 269 and UL 1449 3rd standard. We also offer surge protection devices

for cable/satellite and Ethernet protection since surges are not isolated to the utility lines only.

Product selection Combination of Surge Protection and Surge/Breaker Protection

Ideal for applications with limited space in the panel.



Surae




Table 59. Stage 1 Type 2 (point-of-service entrance) residential surge suppression products for Type BR/CH plug-in loadcentres

Connection	Voltage (Vac)	Phase	Frequency (Hz)	Maximum continuous operating voltage (V) <sup>a</sup>	Voltage protection rating b	Nominal discharge current (A) <sup>c</sup>	circuit current rating (A) d	current capacity per phase (A) <sup>e</sup>	Catalogue number
Plug-on to loadcentre bus in Type BR loadcentres	120/240	Single	50/60	200 Line-to-Neutral (L-N) 400 Line-to-Line (L-L)	600 V L-N 1000 V L-L	3000	10,000	18,000	BRSURGE Surge only
Plug-on to loadcentre bus in Type BR loadcentres	120/240	Single	50/60	150 Line-to-Neutral (L-N) 300 Line-to-Line (L-L)	600 V L-N 1000 V L-L	10,000	10,000	36,000	BR230SUR Surge and Breaker
Plug-on to loadcentre bus in Type BR loadcentres	120/240	Single	50/60	150 Line-to-Neutral (L-N) 300Line-to-Line (L-L)	600 V L-N 1000 V L-L	10,000	10,000	36,000	BR250SUR Surge and Breaker
Plug-on to loadcentre bus in Type CH loadcentres	120/240	Single	50/60	150 Line-to-Neutral (L-N) 300 Line-to-Line (L-L)	600 V L-N 1000 V L-L	10,000	10,000	36,000	CH230SUR Surge and Breaker
Plug-on to loadcentre bus in Type CHloadcentres	120/240	Single	50/60	150 Line-to-Neutral (L-N) 300 Line-to-Line (L-L)	600 V L-N 1000V L-L	10,000	10,000	36,000	CH250SUR Surge and breaker

a Maximum continuous operating voltage that may be applied to the device per mode.

b Voltage protection rating is the measured limiting voltage after a surge event.

c Nominal discharge current is the current that the device can withstand for 15 impulses.

 $<sup>\</sup>mbox{\bf d}$  The amount of current the product can withstand under short circuit conditions.

e The maximum one time surge current rating per phase.

Table 60. Stage 1 Type 2 (point-of-service entrance) residential surge suppression products for any loadcentre

Connection	Voltage (Vac)	Phase	Frequency (Hz)	Maximum continuous operating voltage (V) <sup>a</sup>	Voltage protection rating b	Nominal discharge current (A) <sup>c</sup>	Short circuit current rating (A) d	Surge current capacity per phase (A) <sup>e</sup>	Catalogue number
Can be attached to the	120/240	Single	60	150 Line-to-Neutral (L-N) 300 Line-to-Line (L-L)	600 V L-N 1000 V L-L 800 V N-G	5,000	22,000	36,000	CHSPT2SURGE
outside of any manufacturer's loadcentre (breaker box).	120/240	Single	60			20,000 f	22,000	108,000	CHSPT2ULTRA
This product should be connected on the load side of the loadcentre main service disconnect through a dedicated circuit breaker (follow CEC guidelines).	120/240	Single	60	_	600 V L-G	20,000 f	22,000	108,000	CHSPT22PACK

a Maximum continuous operating voltage that may be applied to the device per mode.

#### Accessories



**CHSPCABLE** 

Table 61. Residential surge suppression accessories


Description	Application	Product warranty	equipment warranty	surge current (A) <sup>a</sup>	Catalogue number
SurgeCable™	Cable TV, satellite, cable modems (2 lines)	Lifetime	\$10,000	20,000	CHSPCABLE
Flushmount Kit™	Flush mount kit for finished wall installations	_	N/A	N/A	CHSPFMKIT

 $<sup>\</sup>boldsymbol{a}$  Maximum surge rating is the sum of all modes of protection.

#### Installation

CHSP and accessories can be mounted on the side, top, or bottom of a circuit breaker panel.

**Note:** CHSP SURGE, ULTRA or the 2-pack can be used interchangeably depending on protection required.



b Voltage protection rating is the measured limiting voltage after a surge event.

c Nominal discharge current is the current that the device can withstand for 15 impulses.

 $<sup>\</sup>ensuremath{\mathbf{d}}$  The amount of current the product can withstand under short circuit conditions.

e The maximum one time surge current rating per phase.

 $<sup>{\</sup>bf f}$  When used with a 50 A two-pole breaker, 10 kA when used with a 15 A two-pole breaker.

g CHSPT22PACK contains one each of CHSPT2ULTRA, CHSPCABLE.

## Street lighting panels

#### In-pole



## Service entrance approved street and roadway lighting panels

- Compact in-pole panel fits into lighting pole hand well
- Pedestal mount 3R (rain-tight) street lighting panels feature a Eaton loadcentre housed in a Pencell enclosure

#### Product description

Since January 1, 2003 the Ontario Electric Safety Code requires that all roadway lighting shall meet the service entrance requirements of Rule 30-1002. Eaton has developed several designs of approved products to suit the various installation points (pole mounted, within an enclosure etc.). All products are CSA approved.

#### In-pole street lighting panels

- Fits into most pole manufacturers' hand well
- · Service entrance approved
- 3R rain-tight
- · Pre-wired
- Single- or two-pole, 22 kA, 50 A versions
- Removable mounting plates accommodate multiple hand wells
- · CSA approved
- Approximate dimensions 9 x 2.25 x 4 inches
- Line power connections via #6 AWG conductor pigtail
- Load power connections via #14 AWG conductor pigtail
- #6 AWG conductor pigtail provided for daisy chaining of additional light poles

#### Product selection

#### Table 62. In-pole street lighting panels

Description	Voltage (Vac)	Main circuit breaker	Interrupting (kAIC)	Catalogue number
120 Vac in-pole compact street lighting panel	120	Single-pole 15 A	22	1SL150PC0
120 Vac in-pole compact street lightning panel	120	Single-pole 30 A	22	1SL300PC0
120 Vac in-pole compact street lighting panel	120	Single-pole 50 A	22	1SL500PC0
240 Vac in-pole compact street lighting panel	120/240	Two-pole 15 A	22	2SL150PC0
240 Vac in-pole compact street lighting panel	120/240	Two-pole 30 A	22	2SL300PC0
240 Vac in-pole compact street lighting panel	120/240	Two-pole 50 A	22	2SL500PC0

#### **Pedestal**

## Pedestal mounted street lighting panels

- · Lightweight, stand-alone units mount on the ground
- Polyethylene Pencell enclosure provides rugged, low profile, rain-tight assembly
- · Penta head and key lock provision for security
- Vented or non-vented enclosure styles
- Two extra 1-inch breaker locations accept Type BR and DNPL plug-in circuit breakers for additional lighting loads
- Service entrance approved
- 3R rain-tight
- Single- or two-pole 22 kA, 50, 60, or 70 A versions
- · CSA approved
- Underground duct or direct burial cable accessible







Vented

#### Product selection

#### Table 63. Pedestal mount non-vented street lighting panels

Voltage (Vac)	Main circuit breaker	Interrupting (kAIC)	Branch circuits (1-inch/½-inch)	Extension	Main circuit breaker wire size range (Cu/Al 60°C or 75°C) (AWG)	Catalogue number
120	Single-pole 50 A	22	2/4	No	#14-4	1SL502NV
120	Single-pole 60 A	22	2/4	No	#4-1/0	1SL602NV
120	Single-pole 70 A	22	2/4	No	#4-1/0	1SL702NV
120/240	Two-pole 50 A	22	2/4	No	#14-4	2SL502NV
120/240	Two-pole 60 A	22	2/4	No	#4-1/0	2SL602NV
120/240	Two-pole 70 A	22	2/4	No	#4-1/0	2SL702NV
120	Single-pole 50 A	22	2/4	Yes	#14-4	1SL502NVE
120	Single-pole 60 A	22	2/4	Yes	#4-1/0	1SL602NVE
120	Single-pole 70 A	22	2/4	Yes	#4-1/0	1SL702NVE
120/240	Two-pole 50 A	22	2/4	Yes	#14-4	2SL502NVE
120/240	Two-pole 60 A	22	2/4	Yes	#4-1/0	2SL602NVE
120/240	Two-pole 70 A	22	2/4	Yes	#4-1/0	2SL702NVE

Table 64. Pedestal mount vented street lighting panels

Voltage (Vac)	Main circuit breaker	Interrupting (kAIC)	Branch circuits (1-inch/½-inch)	Extension	Main circuit breaker wire size range (Cu/Al 60 °C or 75 °C) (AWG)	Catalogue number
120	Single-pole 50 A	22	2/4	Yes	#14-4	1SL502VE
120	Single-pole 60 A	22	2/4	Yes	#4-1/0	1SL602VE
120	Single-pole 70 A	22	2/4	Yes	#4-1/0	1SL702VE
120/240	Two-pole 50 A	22	2/4	Yes	#14-4	2SL502VE
120/240	Two-pole 60 A	22	2/4	Yes	#4-1/0	2SL602VE
120/240	Two-pole 70 A	22	2/4	Yes	#4-1/0	2SL702VE

## Combined loadcentre and meter socket

#### Combined loadcentre and meter socket

- 4 Jaw, 100 and 200 A, 120/240 V, 22 kAIC
- Service entrance rated with 100 or 200 A main circuit breaker included
- · Suitable for underground or overhead service entrance
- Meter socket mechanical lugs accommodate #6–250 MCM Cu/Al line conductors and (2) #6–300 MCM Cu/Al neutral conductors
- Loadcentre mechanical lugs load and neutral (2) #6–300 MCM Cu/Al
- CSR circuit breaker mechanical load lugs #2-300 MCM
- Suitable for overhead or underground service entrance
- Suitable applications include farming, temporary service, construction sites, trailers, and mobile homes
- Hub opening and plate included. Hubs ordered separately (use DS type hubs)
- 3R enclosure
- · CSA approved



#### Product selection


#### Table 65. Combined loadcentre and meter socket

Enclosure	Voltage (V)	Amperage (A)	Interrupting (kAIC)	Entrance type	Branch circuits (1-inch/½-inch)	Weight in lb (kg)	Dimensions in inches (mm)	Catalogue number
Indoor/outdoor Type 3R	120/240	100	22	Underground/overhead	8/16	36.5 (16.6)	28.38 x 14.44 x 5.38 (974.7 x 366.7 x 136.5)	RCPM108M
Indoor/outdoor Type 3R	120/240	200	22	Underground/overhead	8/16	36.5 (16.6)	28.38 x 14.44 x 5.38 (974.7 x 366.7 x 136.5)	RCPM208M


## Table 66 Knockout legend

Location	Knockout size in inches (mm)	Quantity
Bottom end wall	0.50 (12.7)	7
Bottom end wall	0.50, 0.75 (12.7, 19.1)	4
Bottom end wall	0.50, 0.75, 1.00 (12.7, 19.1, 25.4)	1
Bottom end wall	1.00, 1.25, 1.50, 2.00 (25.4, 31.8, 38.1, 50.8)	1
Bottom end wall	1.25, 1.50, 2.00, 2.50, 3.00 (31.8, 38.1, 50.8, 63.5, 76.2)	1
Top end wall	Provision for Hub a (e.g. DS200H2, DS250H2, DS300H2)	2
Backplane	1.25, 1.50, 2.00, 2.50 (31.8, 38.1, 50.8, 63.5)	1
Backplane	1.25, 1.50, 2.00 (31.8, 38.1, 50.8)	1
Right sidewall	1.25, 1.50, 2.00, 2.50 (31.8, 38.1, 50.8, 63.5)	1

a Accommodate Type DS conduit hubs. Hubs not included. See  ${\bf page\ 15}$  for selection.



Top Surface



## Metered temporary ground fault power panel

## Metered temporary power panel with ground fault protection

- Combination loadcentre, meter socket, and electrical outlets for temporary work site installations
- · Single-phase, three-wire
- 4 jaw, 100 or 200 A, 120/240 V, 22 kAIC meter socket
- · Suitable for overhead or underground service entrance
- CSA approved for service entrance
- 3R enclosure suitable for outdoor installations
- Two different receptacle combinations 6X20A and 2X30A or 10X20A
- Hub opening and plate included. Hubs ordered separately (uses DS type hubs)
- Meter socket mechanical lugs accommodate #6–250 MCM Cu/Al line conductors and #6–300 MCM Cu/Al neutral conductors



## Product selection

Table 67. Metered temporary ground fault protected power panel

Enclosure	Voltage (V)	Amperage (A)	Interrupting (kAIC)	Entrance Type	20 A receptacles	30 A receptacles	Dimensions in inches (mm)	Catalogue number
Indoor/outdoor Type 3R	120/240	100	22	Underground/overhead	6	2	34.38 x 22.00 x 5.38 (873.1 x 558.8 x 136.5)	RCPM1GF6H
Indoor/outdoor Type 3R	120/240	100	22	Underground/overhead	10	0	34.38 x 22.00 x 5.38 (873.1 x 558.8 x 136.5)	RCPM1GF10
Indoor/outdoor Type 3R	120/240	200	22	Underground/overhead	6	2	34.38 x 22.00 x 5.38 (873.1 x 558.8 x 136.5)	RCPM2GF6H
Indoor/outdoor Type 3R	120/240	200	22	Underground/overhead	10	0	34.38 x 22.00 x 5.38 (873.1 x 558.8 x 136.5)	RCPM2GF10


## Table 68. Knockout legend

Catalogue number	Knockout size (inches)	Quantity
Bottom endwall	0.50, 0.75	6
Bottom endwall	0.50, 0.75, 1.00, 1.25	2
Bottom endwall	1.00, 1.25, 1.50, 2.00, 2.50	1
Bottom endwall	1.00, 1.25, 1.50, 2.00, 2.50, 3.00	1
Top endwall	Provision for Hub a (e.g. DS200H2, DS250H2, DS300H2)	1

a Accommodate Type DS conduit hubs. Hubs not included. See page 13 for selection.



Top Surface



#### Mini-power centres



#### Mini-power centres

- Distribution transformer, breaker protection, and loadcentre all in one compact package
- Primary and secondary breaker protection via factory installed EHD or FDB type MCCBs
- 18, 25, or 35 kAIC interrupting capacity versions available on select models through special order
- Two styles of interior; one for plug-in or bolt-on (breakers not included)
- Loadcentre accommodates up to 24 feeder circuit breakers (breakers purchased separately)
- Aluminum chassis on plug-in type, copper chassis on bolt-on type, standard ground bar, and enclosure grounded neutral bar
- All live parts are enclosed
- Hinged, padlockable cover prevents removal
- Enclosure includes grounding terminal
- Type 3R enclosure with baked polymer polyester powder coating is good for indoor or outdoor mounting
- Optional Type 3R, 316 grade stainless steel enclosure
- Main circuit breaker barrier provides CSA approval for service entrance applications
- Electrical grade aluminum windings standard on the distribution transformer (copper optional)
- Copper windings standard on bolt-on style units
- 185 °C insulation system
- 115 °C winding temperature rise
- Full capacity taps (FCBN) 2-5%
- Resin encapsulated, core-coil assembly (cores grounded with copper lead)

#### Product description


Contemporary electrical distribution systems are required to do more in less space while at the same time being cost-effective. Eaton provides a solution to these requirements with the proven mini-power centre. It occupies considerably less space and can save up to 31 percent of the installation costs normally required when individual components are used. The solution is possible because a mini-power centre combines three individual components into one NEMA Type 3R enclosure: a main breaker, an encapsulated Type EP or EPT dry-type transformer, and a secondary distribution loadcentre with main breaker. Interconnecting wiring is completed at the factory. A mini-power centre is delivered ready for installation. It's suitable for use as service entrance equipment, too. Mini-power centres are used wherever there is a 480 V or 600 V distribution system and loads requiring 208Y/120 V three-phase or 120/240 V single-phase.

Typical installations include:

- · Industrial plant assembly lines
- Plant expansions
- Commercial buildings
- Test equipment
- Temporary power at construction sites
- Sewage disposal plants
- Warehouses
- Car washes
- · Parking lots

The mini-power centre saves you space, time, and money. A minipower centre installation takes up only 42% of the space taken up by a typical installation. A typical installation being comprised of a separately mounted distribution transformer, disconnect switch, loadcentre and all associated wiring and connectors.

The installation costs of a mini-power centre are 31% less when compared with the same typical installation.



15 kVA, three-phase

15 kVA, three-phase

#### Time to perform task(s) a (hours)

	Typical installation	Mini-power centre installation	Typical installation	Mini-power centre installation
Installation	15 kVA	15 kVA	25 kVA	25 kVA
Switch and fuse mounting	5	0	5	0
Transformer layout (remove knockout, etc.)	16	16	24	24
Fasten transformer to wall	4	0	4	0
Layout loadcentre, mount and connect source	4	4	6	4
Total hours	29	20	39	28
% time saved by using a eaton mini-power centre		31%		28%

## Plug-in

Table 69. Single-phase plug-in mini-power centres

	Primary and		Maximum number of Main circuit breaker b feeder circuit breakers Dimensions in inches (mm) c		<b>m)</b> c							
kVA	secondary voltage (V)	Catalogue number a	Primary	Secondary	Single- pole	Two- pole	Three- pole	Maximum amperage	Height	Width	Depth	Weight in Ib (kg)
3	480 to 120/240	P48G11S03P	EHD2015	BR215	8	4	_	12	27.05 (699.0)	12.60 (320.0)	9.70 (245.0)	105 (47)
5	480 to 120/240	P48G11S05P	EHD2020	BR225	12	6	_	20	29.50 (749.0)	12.60 (320.0)	9.70 (245.0)	105 (47)
7.5	480 to 120/240	P48G11S07P	EHD2030	BR230	12	6	_	30	29.50 (749.0)	12.60 (320.0)	9.70 (245.0)	125 (56)
10	480 to 120/240	P48G11S10P	EHD2040	BR250	12	6	_	40	38.20 (970.0)	13.50 (343.0)	11.80 (300.0)	177 (80)
15	480 to 120/240	P48G11S15P	EHD2060	BR270	20	10	_	60	38.20 (970.0)	13.50 (343.0)	11.80 (300.0)	212 (96)
25	480 to 120/240	P48G11S25P	EHD2100	BR2125	26	13	_	100	43.90 (1115.0)	16.40 (417.0)	11.80 (300.0)	373 (169)
5	600 to 120/240	P60G11S05P	FDB2015	BR225	12	6	_	20	29.50 (749.0)	12.60 (320.0)	14.60 (370.0)	105 (47)
7.5	600 to 120/240	P60G11S07P	FDB2030	BR230	12	6	_	30	29.50 (749.0)	12.60 (320.0)	9.70 (245.0)	125 (56)
10	600 to 120/240	P60G11S10P	FDB2040	BR250	12	6	_	40	38.20 (970.0)	13.50 (343.0)	9.70 (245.0)	177 (80)
15	600 to 120/240	P60G11S15P	FDB2060	BR270	20	10	_	60	38.20 (970.0)	13.50 (343.0)	11.80 (300.0)	212 (96)
25	600 to 120/240	P60G11S25P	FDB2100	BR2125	26	13	_	100	43.90 (1115.0)	16.40 (417.0)	14.60 (370.0)	373 (169)

a For a primary main circuit breaker interrupting capacity greater than 10 kAlC, add the following suffixes to the catalogue number; for 18 kAlC, add "F"; for 25 kAlC, add "H"; and for 35 kAlC, add "C".

**Note**: For price and delivery on a unit with copper transformer windings or 316 grade stainless steel enclosure, contact your local Eaton sales representative or our Customer Service centre at 1-800-268-3578. Feeder circuit breakers not included. Uses Eaton Type BR circuit breakers.

Table 70. Three-phase plug-in mini-power centres

	Primary and		Main circuit breaker b		feeder circuit breakers			Dimensions in inches (mm) <sup>c</sup>			_	
kVA	secondary Catalogue voltage (V) number a	Catalogue number <sup>a</sup>	Primary	Secondary	Single- pole	Two- pole	Three- pole	Maximum amperage	Height	Width	Depth	Weight in lb (kg)
15	480 to 120/208	P48G28T15P	EHD3040	BR350	18	9	6	40	36.10 (917.0)	28.80 (732.0)	9.70 (245.0)	320 (145)
22.5	480 to 120/208	P48G28T21P	EHD3070	BR370	18	9	6	60	40.90 (1039.0)	29.90 (759.0)	11.80 (300.0)	565 (256)
30	480 to 120/208	P48G28T30P	EHD3090	BR3100	24	12	8	80	41.90 (1064.0)	29.90 (759.0)	13.60 (346.0)	635 (288)
15	600 to 120/208	P60G28T15P	FDB3030	BR350	18	9	6	40	36.10 (917.0)	28.80 (732.0)	9.40 (238.0)	320 (145)
22.5	600 to 120/208	P60G28T21P	FDB3050	BR370	18	9	6	60	40.90 (1039.0)	29.90 (759.0)	5650 (256.0)	565 (256)
30	600 to 120/208	P60G28T30P	FDB3070	BR3100	24	12	8	80	41.90 (1064.0)	29.90 (759.0)	6350 (288.0)	635 (288)

a For a primary main circuit breaker interrupting capacity greater than 10 kAIC, add the following suffixes to the catalogue number; for 18 kAIC add "F", for 25 kAIC add "H", and for 35 kAIC add "C".

**Note:** For price and delivery on a unit with copper transformer windings or 316 grade stainless steel enclosure, contact your local Eaton sales representative or our Customer Service centre at 1-800-268-3578. Feeder circuit breakers not included. Uses Eaton Type BR circuit breakers.

b Main circuit breakers fixed only. No substitutes.

c Not for construction purposes.

b Main circuit breakers fixed only. No substitutes.

c Not for construction purposes.

## **Bolt-on mini-power centres**

## **Bolt-on**

Table 71. Single-phase bolt-on mini-power centres

	Primary and		Main circu	uit breaker a	Maximum number of feeder circuit breakers				Dimensions			
kVA	secondary voltage (V)	Catalogue number	Primary	Secondary	Single- pole	Two- pole	Three- pole	Maximum amperage	Height	Width	Depth	Weight in lb (kg)
3	480 to 120/240	P48G11S03CUB	EHD2015L	BAB2015	12	6	_	12	33.20 (845.0)	12.60 (320.0)	9.70 (245.0)	105 (47)
5	480 to 120/240	P48G11S05CUB	EHD2020L	BAB2025	18	9	_	20	36.10 (918.0)	12.60 (320.0)	9.70 (245.0)	110 (50)
7.5	480 to 120/240	P48G11S07CUB	EHD2030L	BAB2030	18	9	_	30	36.10 (918.0)	12.60 (320.0)	9.70 (245.0)	110 (50)
10	480 to 120/240	P48G11S10CUB	EHD2040L	BAB2050	18	9	_	40	40.90 (1038.0)	13.50 (343.0)	11.80 (300.0)	180 (82)
15	480 to 120/240	P48G11S15CUB	EHD2060L	BAB2070	24	12	_	60	43.90 (1115.0)	15.00 (380.0)	11.80 (300.0)	215 (98)
25	480 to 120/240	P48G11S25CUB	EHD2100L	BAB2125	30	15	_	100	43.40 (1102.0)	20.40 (518.0)	14.60 (370.0)	385 (175)
3	600 to 120/240	P60G11S03CUB	FDB2015L	BAB2015	12	6	_	12	33.20 (845.0)	12.60 (320.0)	9.70 (245.0)	105 (47)
5	600 to 120/240	P60G11S05CUB	FDB2020L	BAB2025	18	9	_	20	36.10 (918.0)	12.60 (320.0)	9.70 (245.0)	110 (50)
7.5	600 to 120/240	P60G11S07CUB	FDB2030L	BAB2030	18	9	_	30	36.10 (918.0)	12.60 (320.0)	9.70 (245.0)	110 (50)
10	600 to 120/240	P60G11S10CUB	FDB2040L	BAB2050	18	9	_	40	40.90 (1038.0)	13.50 (343.0)	11.80 (300.0)	180 (82)
15	600 to 120/240	P60G11S15CUB	FDB2060L	BAB2070	24	12	_	60	43.90 (1115.0)	15.00 (380.0)	11.80 (300.0)	215 (98)
25	600 to 120/240	P60G11S25CUB	FDB2100L	BAB2125	30	15	_	100	43.40 (1102.0)	20.40 (518.0)	14.60 (370.0)	385 (175)

a Main circuit breakers fixed only. No substitutes.

Table 72. Three-phase bolt-on mini-power centres

Primary and			Main circuit breaker a		Maximum number of feeder circuit breakers bc				Dimensions in inches (mm) d			_
kVA	secondary voltage (V)	Catalogue number	Primary	Secondary	Single- pole	Two- pole	Three- pole	Maximum amperage	Height	Width	Depth	Weight in lb (kg)
15	480 to 120/208	P48G28T15CUB	EHD3040L	BAB3050H	18	9	6	40	36.10 (917.0)	28.70 (730.0)	9.40 (238.0)	320 (148)
22.5	480 to 120/208	P48G28T21CUB	EHD3070L	BAB3070H	18	9	6	60	40.90 (1038.0)	29.90 (759.0)	13.60 (346.0)	565 (257)
30	480 to 120/208	P48G28T30CUB	EHD3090L	BAB3100H	24	12	8	80	41.90 (1063.0)	29.90 (759.0)	13.60 (346.0)	635 (288)
15	600 to 120/208	P60G28T15CUB	FDB3030	BAB3050H	18	9	6	40	36.10 (917.0)	28.70 (730.0)	9.40 (238.0)	320 (148)
22.5	600 to 120/208	P60G28T21CUB	FDB3050	BAB3070H	18	9	6	60	40.90 (1038.0)	29.90 (759.0)	13.60 (346.0)	565 (257)
30	600 to 120/208	P60G28T30CUB	FDB3070	BAB3100H	24	12	8	80	41.90 (1063.0)	29.90 (759.0)	13.60 (346.0)	635 (288)

a Main circuit breakers fixed only. No substitutes.

b Feeder circuit breakers not included. Uses Eaton Type BAB circuit breakers.

c Combinations can be selected.

d Not for construction purposes.

b Feeder circuit breakers not included. Uses Eaton Type BAB circuit breakers.

c Combinations can be selected.

d Not for construction purposes.

## **Residential fuse panel inserts**

#### Residential fuse panel inserts -

- Convenient and economical option to completely replacing an entire fuse panel assembly
- Original fuse panel tub and wiring remains in place and only the fuse panel trim and interior is removed and replaced
- 16 and 24 circuit breaker interiors designed to fit any manufacturers' fuse panel or discontinued design circuit breaker panel
- · Custom trim and door oversized to ensure fit with existing tub
- Circuit breaker interior replacement eliminates the possibility of improperly sized amperage protection
- No more loose fuses causing arcing and damage to the panel or wiring
- CSA certified to mount into any existing box under file LL264-222
- Can be mounted in any orientation as defined by the existing fuse panel tub orientation
- Accepts plug-in Type BR, DNPL, or GFCB circuit breakers (circuit breakers sold separately, refer to page 17 to page 20 for selection)
- Trim comes complete with hinged door, non-locking spring latch, clear plastic card holder, and circuit directory card
- · Tin plated aluminum bus bars
- a Not for use as service entrance equipment

#### Product description

Fuses and fuse panels were designed decades ago, to prevent the overload of circuit wiring that could lead to fires caused by overloaded electrical circuit connections and/or short circuits. Records show however, that problems of fire and smoke inhalation are the more serious causes of death or injury.

Since early 1960's, technology has allowed a tremendous increase in the number and use of appliances, tools, and control systems, many of which are automatically controlled and cycle on and off. We now know that a cycling load will actually cause a plug (screwon-type) fuse to loosen in its holder (that explains why you can always find one or two fuses that can be tightened a quarter turn). Loose connections such as these develop heat, and in turn increase the risk of fire.

Small overloads can be absorbed by the margin of safety built into CSA certified devices. However, prolonged overloads or loose fuses will cause arcing and ultimately, melting of the connections in either the panel or wiring, wherever the weakest link may be.

Eaton has designed a low cost method of replacing fuse panels with modern circuit breaker panels. This method eliminates the need for cutting, re-plastering and repainting the walls around the old panel.

Another risk with the old fuse panel design was the ease with which incorrect fuses could be used or changed without realization of the risks involved.

To eliminate these potential hazards Eaton has a new circuit breaker interior and trim kit that will quickly upgrade the existing installation to today's electrical standards and needs. An average upgrade takes one hour and thus creates the minimum of inconvenience to the homeowner/occupant.

#### Sample specification

- Supply and install a new circuit breaker interior to replace existing plug fuse panel interior or out of date circuit breaker interior in each apartment or condominium
- Interior to be 16 or 24 circuit, rated 100 A and 120/240 V, designed in a single row breaker arrangement for fitting into existing recessed electrical panels
- Supply and install new trim and door assembly slightly larger then discarded fuse trim to minimize any requirements for patching or repainting
- Bus bars shall be tin plated aluminum suitable for plug-in circuit breakers
- Supply and install a trim and door assembly with latch, to protect the circuit breaker toggle handles
- Inserts must be CSA certified for mounting in any position, for ease in connecting to existing wiring
- Install circuit breakers with ratings as indicated in specifications or drawings
- Interiors to be mounted with directions template and hardware supplied by Eaton
- Inserts, trim and door assembly and circuit breakers, shall be manufactured by Eaton
- Provide a circuit identification card, mounted under clear plastic on the inside of the door

## Residential fuse panel inserts

#### **Insert interiors**

#### Residential fuse panel insert interiors

- 100 A single-phase, three-wire 120/240 Vac
- 16 and 24 circuit breaker capacity a
- CSA certified to mount into any existing box under file LL264-222
- Accepts plug-in type BR and DNPL circuit breakers ab
- Tin plated aluminum bus bars
- Neutral available with 16 or 24 Cu/Al terminals
- · Main and neutral lugs located at the same end
- All terminals accept #14-3 AWG cabling
- a Filler plates for unused fuse panel insert circuit breaker installation locations can be ordered as BRFP (package of 24).

b Refer to page 17 to page 20 for plug-in circuit breaker selection.





Table 73. Three-wire 120/240 Vac fuse panel insert interiors

Number	of	installable

		Circuit breakers	•					
Amperage rating (A)	Voltage (V)	1-inch spaces	1/2-inch spaces	Bus material	Neutral material	Wire size range Cu/Al	Catalogue number	Drilling template catalogue number a
100	120/240	8	16	Aluminum	Aluminum	#14-3 AWG	CQLP8100	CSABP4683B
100	120/240	12	24	Aluminum	Aluminum	#14-3 AWG	CQLP12100	CSABP4734B

a We suggest the use of templates to ensure proper sizing for installation.




## Residential fuse panel inserts

#### **Trims**

#### Residential fuse panel insert trims

- Doors are die formed with sloping sides and rounded corners and permanently mounted to the trim
- Semi concealed hinges a
- Includes circuit directory card and self adhesive clear plastic directory holder
- Painted ASA61 light grey baked on enamel
- Mounting hardware included b
- Trims are custom sized larger than the existing trim and door
- Trim mounting holes located to line up with existing box holes c
- $\boldsymbol{a}$  If the main service entrance is bottom entry, the door hinges left. If it is top entry, then the door hinges right.
- b The hardware supplied will accommodate boxes that are mounted up to 1/2-inch too deep or equal to 3-1/2 inches net depth.
- c Measure the existing box holes locations as they may be part of the end walls, side walls, or tapped into a box flange.



## Table 74. Fuse panel insert trims

Original ca	Fuse panel	Box dimensions (inches)		Replacement trim	Trim size	е	Replacement interior		Trim mounting holes (inches)	
	catalogue number	Height	Width	Depth	catalogue number	Height	Width	catalogue number	Height	Width
Amalgamated	4112	16-1/8	8-1/2	2-15/16	QLPT16D	18-1/4	9-3/4	CQLP8100	16-1/6	4
Amalgamated	4116	19-1/2	8-1/2	2-15/16	QLPT19D	20-7/8	9-3/4	CQLP8100	18-11/16	4
Amalgamated	4120	22-7/8	8-1/2	2-15/16	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6
Amalgamated	4208	16-1/8	8-1/2	2-15/16	QLPT16AD	18-1/4	10-5/16	CQLP8100	15-1/2	6
Amalgamated	4212	19-1/2	8-1/2	2-15/16	QLPT20AD	20-7/8	9-3/4	CQLP8100	18-11/16	6
Amalgamated	4216	22-7/8	8-1/2	2-15/16	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6
Amalgamated	4220	24-1/8	8-1/2	2-15/16	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
Amalgamated	4312	22-7/8	8-1/2	2-15/16	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6
CEB	NHP10-636-3 b	24	10	3	QLPT24LD	26	12	CQLP12100 a	23-13/16	4
CEB	NHP6-60 c	14	7-3/4	3	QLPT14D	16	9-3/4	CQLP8100	13-3/16	4
CEB	NHP12-60	20	7-3/4	3	QLPT20D	21-3/4	9-3/4	CQLP12100 a	19-9/16	4
CEB	NHP12-633	23	7-3/4	3	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
CEB	NHP4-632	16-1/4	7-3/4	3	QLPT16D	18-1/4	9-3/4	CQLP8100	16-1/6	4
CEB	NHP6-633	20	7-3/4	3	QLPT19D	20-7/8	9-3/4	CQLP8100	18-11/16	4
CEB	NHP6-636-4	24	7-3/4	3	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
CEB	NHP8-60	16-1/8	7-3/4	3	QLPT16D	18-1/4	9-3/4	CQLP8100	16-1/6	4
CEB	NHP8-635-3	23	7-3/4	3	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
Taylor (Crouse-Hinds)	NHP6-30-60	21	7-3/8	3	QLPT20D	21-3/4	9-3/4	CQLP12100 a	19-9/16	4
Taylor (Crouse-Hinds)	NHP20-1231	24-1/2	9-1/2	3	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
Taylor (Crouse-Hinds)	NHP20-0821-6	24-1/2	9-1/2	3	QLPT24D	26	9-3/4	CQLP12100 a	23-13/16	4
Taylor (Crouse-Hinds)	NHP12B-1000-2	17-1/8	9-1/2	3	QLPT16AD	18-1/8	10-5/16	CQLP8100	15-1/2	6
Taylor (Crouse-Hinds)	NHP10-0401-4	17-1/8	9-1/2	3	QLPT16AD	18-1/8	10-5/16	CQLP8100	15-1/2	6
Taylor (Crouse-Hinds)	NHP10-0601-2	17-1/8	9-1/2	3	QLPT16AD	18-1/8	10-5/16	CQLP8100	15-1/2	6
Taylor (Crouse-Hinds)	NHP10-0611	17-1/8	9-1/2	3	QLPT16AD	18-1/8	10-5/16	CQLP8100	15-1/2	6
Taylor (Crouse-Hinds)	NHP10-0801	17-1/8	9-1/2	3	QLPT16AD	18-1/8	10-5/16	CQLP8100	15-1/2	6
Taylor (Crouse-Hinds)	NHP12-0811	19-1/4	9-1/2	3	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6
Taylor (Crouse-Hinds)	NHP14-0801-4	19-1/4	9-1/2	3	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6
Taylor (Crouse-Hinds)	NHP14-0621-2	19-1/4	9-1/2	3	QLPT22AD	25	10-1/2	CQLP12100 a	22-1/4	6

a Panel insert CQLP8100 can also be used with this size trim.

b For box sizes either 26 inches or 27-1/2 inches high, no insert or trim is available.

c For box size 14" only

## **Bolt-on Type BQL single-, multi-pole, Duplex, and Quadplex**

## Type BQL a

- 10,000/22,000 A interrupting capacity at 120/240 Vac
- Captive line screw included (#2 Robertson/Slot)

a HACR rated.

#### Product selection

Table 75. Single- and multi-pole bolt-on classic replacement circuit breakers

		Catalogue number						
Атроно	Wire size range (Cu/AI 60 °C or	Single-pole, 120/240 Vac		Two-pole, 120/240 Vac	Three-pole, 1	20/240 Vac		
Ampere rating	75 °C) (AWG)	10 kAIC	22 kAIC	10 kAIC	10 kAIC	22 kAIC		
15	#14-8	BQL15 a	HBQL15	BQL215	BQL315	HBQL315		
20	#14-8	BQL20 a	HBQL20	BQL220	BQL320	_		
25	#14-8	BQL25	HBQL25	BQL225	_	_		
30	#14-8	BQL30	HBQL30	BQL230	BQL330	HBQL330		
10	#14-4	BQL40	HBQL40	BQL240	BQL340	_		
50	#14-4	BQL50	HBQL50	BQL250	BQL350	HBQL350		
10	#8-2/0	BQL60	HBQL60	BQL260	BQL360	HBQL360		
'0	#8-2/0	_	_	BQL270	BQL370	HBQL370		
10	#8-2/0	_	_	BQL290	BQL390	HBQL390		
00	#8-2/0	_	_	BQL2100	BQL3100	HBQL3100		
25	#8-2/0	_	_	BQL2125	_	_		
35	#8-2/0	_	_	BQL2135	_	_		
		Requires one 1-i	nch (25.4 mm) space	Requires two 1-inch (25.4 mm) space	Requires three 1	-inch (25.4 mm) spaces		

a Switching duty rated (SWD).

## Type BQL Duplex and Quadplex a

- 10,000 A interrupting capacity at 120/240 Vac
- Captive line screw included (#2 Robertson/Slot)

① HACR rated.

Table 76. Type BQL Duplex and Quadplex bolt-on classic replacement circuit breakers

Duplex		Quadplex ind	ependent trip						
Two single	e-pole circuits	Two single-p	ole circuits an	d one two-pol	e circuit	Two two-pol	e circuits		_
Ampere ra	ating	Ampere ratin	g			Ampere rati	ng		_
		120 Vac	120/240 Vac	120 Vac		120/240 Vac			Wire size
120 Vac	Catalogue number	Outer left (single-pole)	Centre (two-pole)	Outer right (single-pole)	Catalogue number	Outer left and right (two-pole)	Centre (two-pole)	range (Cu/A re Catalogue 60 °C or	range (Cu/Al
15–15	BQLT15 a	15	15	15	BQLT15215	15	15	BQLT215215	#14-4
20-20	BQLT20 a	15	20	15	BQLT15220	20	20	BQLT220220	#14-4
30-30	BQLT30 a	15	25	15	BQLT15225	15	30	BQLT215230	#14-4
_	_	15	30	15	BQLT15230	15	40	BQLT215240	#14-4
_	_	15	40	15	BQLT15240	_	_	_	#14-4
Requires on	e 1-inch (25.4 mm) space	Requires two 1-	inch (25.4 mm) s	paces		Requires two 1	-inch (25.4 mm) spa	ices	

a Switching duty rated (SWD).

## Bolt-on Type BQL ground fault and moulded case switches

## Type BQL ground fault circuit breakers

- 10,000 A interrupting capacity at 120/240 Vac
- 5 mA "people protection"

#### Product selection

5 mA single- and two-pole bolt-on ground fault circuit breakers are no longer able to be manufactured due to change in UL standard to require all GF devices to "Self Test".

#### Type BQL non-automatic circuit breakers (moulded case switches)

- 240 Vac
- Two- and three-pole versions

## Table 77. Two- and three-pole bolt-on non-automatic circuit breakers (moulded case switches)

Атроно	Wire size range Cu/Al	Catalogue number			
Ampere rating	60 °C or 75 °C (AWG)	Two-pole, 240 Vac	Three-pole, 240 Vac		
60	#8-1 Cu #8-1/0 Al	BQL260NA	BQL360NA		
		Requires two 1-inch (25.4 mm) spaces	Requires three 1-inch (25.4 mm) spaces		

**Note:** When the Canadian Electrical Code requires the use of an unfused disconnect device as a local isolation switch, then a circuit breaker enclosure may be used in conjunction with a moulded case switch (a.k.a. a non-automatic circuit breaker). For example, with an air conditioning unit, the protective device for these applications is located upstream.

## Bolt-on Type QBH single- and multi-pole.

## Type QBH

- 120/240 Vac
- 3/4-inch form factor
- · Designed to fit the classic CEB, Sylvania or Commander Electric design bolt-on loadcentres
- Suitable for loadcentres, lighting and distribution panelboards, and meter centres
- Silver Tungsten contacts with wiping action to prevent carbon buildup on the contact surface
- Handle provides clear indication of ON/OFF/TRIPPED position
- Quick-make / quick-break mechanism provides tease-proof operation
- Internal common trip mechanism on two-pole circuit breakers
- Each breaker is electronically calibrated for 40 °C
- Compression moulded housing and handle for durability and service

Table 78. Single- and two-pole bolt-on classic replacement circuit breakers

		Catalogue number	
Атпоно	Wire size renge	Single-pole, 120 Vac	Two-pole, 120/240 Vac
Ampere rating	Wire size range 60 °C or 75 °C (AWG)	10 kAIC	10 kAIC
15	#14-10 Cu, #12-10 Al	QBH15	QBH215
20	#14-10 Cu, #12-10 Al	QBH20	QBH220
25	#14-10 Cu, #12-10 Al	QBH25	QBH225
30	#10-2 Cu, #10-1 AI	QBH30	QBH230
40	#10-2 Cu, #10-1 AI	QBH40	QBH240
50	#10-2 Cu, #10-1 AI	QBH50	QBH250
60	#10-2 Cu, #10-1 AI	QBH60	QBH260
70	#10-2 Cu, #10-1 AI	_	QBH270
90	#10-2 Cu, #10-1 AI	_	QBH290
100	#10-2 Cu, #10-1 AI	_	QBH2100
125	#10-1 Cu	_	QBH2125
		Requires one 3/4-inch (19.1 mm) space	Requires two 3/4-inch (19.1 mm) spaces

## Plug-in Type BJ two- and three-pole

Type BJ a

- Main circuit breakers for classic Westinghouse NovaLine loadcentres
- 10,000 A interrupting capacity at 120/240 Vac
- a BJ breakers are also approved as branch circuit breakers on CPM/CPL panels 200 A and greater.

Table 79. Type BJ two- and three-pole plug-in classic replacement circuit breakers

$c_{a+a}$	loaue	10111100	hou

Ampere rating	Wire size range Cu/Al 60 °C or 75 °C (AWG)	Two-pole, 120/240 Vac 1 per shelf carton 10 kAIC	Three-pole, 120/240 Vac 1 per shelf carton 10 kAIC
125	#2-300 MCM	BJ2125	BJ3125
150	#2-300 MCM	BJ2150	BJ3150
175	#2-300 MCM	BJ2175	BJ3175
200	#2-300 MCM	BJ2200	BJ3200
		Requires four 1-inch (25.4 mm) spaces a	Requires six 1-inch (25.4 mm) spaces b

a When mounted, the Type BJ circuit breakers span both sides of the bus bar occupying an equivalent number of pole spaces on both the left and right side of the loadcentre. For example a two-pole Type BJ circuit breaker occupies 2 pole spaces on the left and the same number of spaces on the right thus requiring four 1-inch spaces.

b When mounted, the Type BJ circuit breakers span both sides of the bus bar occupying an equivalent number of pole spaces on both the left and right side of the loadcentre. For example a three-pole Type BJ circuit breaker occupies 3 pole spaces on the left and the same number of spaces on the right thus requiring six 1-inch spaces.

#### **Pressure switches**

- Ensures smooth delivery of water into your home
- Commercial, residential, or agricultural applications
- Can be used on all types of pumps
- Pressure ratings 20-40 PSI, 30-50 PSI, and 40-60 PSI
- Adjustable cut-in and cut-out pressure
- Easy installation
- · CSA certified and UL listed
- Pulsation plug models prevent pump cycling due to water surges
- Low pressure cut-off models prevent pump burn out due to lack of well water (10 PSI below turn on pressure)
- 3-year product warranty

#### Product selection

#### Table 80. Pressure switches


Description	Enclosure style	Catalogue number
20-40 PSI pressure switch	NEMA 1	CHWPS2040D
20-40 PSI pressure switch with pulsation plug	NEMA 1	CHWPS2040DP
20–40 PSI pressure switch with low pressure cut-off	NEMA 1	CHWPS2040DL
30–50 PSI pressure switch	NEMA 1	CHWPS3050D
30–50 PSI pressure switch with low pressure cut-off	NEMA 1	CHWPS3050DL
40-60 PSI pressure switch	NEMA 1	CHWPS4060D



Phase	Voltage (AC)	Amperage	Horsepower
Single	115	20	1.5
Handle tie	230	12	2.0



Pressure switch



## Table 82. Pressure switch cross-reference

	Catalogue number					
Description	Eaton	Square DT	FlotecT	Water AceT	FurnasT	
20–40 PSI pressure switch	CHWPS2040D	9013FSG2J20	_	15767A510	69WA4Z2040	
20-40 PSI pressure switch with pulsation plug	CHWPS2040DP	9013FSG2J20P	_	_	69WA4Z2040B	
20-40 PSI pressure switch with low pressure cut-off	CHWPS2040DL	9013FSG2J20M4	_	_	69WEC	
30–50 PSI pressure switch	CHWPS3050D	9013FSG2J21	TC2151	15760A501	69WA4	
30–50 PSI pressure switch with low pressure cut-off	CHWPS3050DL	9013FSG2J21M4	FP217-1140	19180A501	_	
40–60 PSI pressure switch	CHWPS4060D	9013FSG2J24	TC2153	_	69WA4Z4060	

#### Notes:

- CSA is a registered trademark of the Canadian Standards Association
- UL is a federally registered trademark of Underwriters Laboratories Inc.
- NEMA Is the registered trademark and service mark of the National Electrical Manufacturers Association
- Square D is a federally registered trademark of Schneider Electric
- Flotec is a registered trademark of Flotec
- Furnas is a registered trademark of Siemens Energy and Automation, Inc.
- Water Ace is a registered trademark of the Pentair Pump Group

## Index

1SL150PCO <b>50</b>	3CCPL103 <b>12</b>	BAB2100 <b>41</b>	BQL230 <b>60</b>
1SL300PCO <b>50</b>	3CPL112 <b>12</b>	BAB2125 <b>41</b>	BQL240 <b>60</b>
1SL500PCO <b>50</b>	3CPL124 <b>12</b>	BAB3015H <b>41</b>	BQL250 <b>60</b>
1SL502NV <b>51</b>	3CPL130 <b>12</b>	BAB3020H <b>41</b>	BQL260 <b>60</b>
1SL502NVE <b>51</b>	3CPL136 <b>12</b>	BAB3030H <b>41</b>	BQL260NA 61
1SL502VE <b>51</b>	3CPL218 <b>12</b>	BAB3040H <b>41</b>	BQL270 <b>60</b>
1SL602NV <b>51</b>	3CPL224 <b>12</b>	BAB3050H <b>41</b>	BQL290 <b>60</b>
1SL602NVE <b>51</b>	3CPL230 <b>12</b>	BAB3060H <b>41</b>	BQL315 <b>60</b>
1SL602VE <b>51</b>	3CPL242 <b>12</b>	BAB3070H <b>41</b>	BQL320 <b>60</b>
1SL702NV <b>51</b>	3CPL442 <b>12</b>	BAB3090H <b>41</b>	BQL330 <b>60</b>
1SL702NVE <b>51</b>	3CPM112 <b>8</b>	BAB3100H <b>41</b>	BQL340 <b>60</b>
1SL702VE <b>51</b>	3CPM130 <b>8</b>	BABF1015 <b>41</b>	BQL350 <b>60</b>
2SL150PCO <b>50</b>	3CPM230 <b>8</b>	BHGW-10 <b>24</b>	BQL360 <b>60</b>
2SL300PCO <b>50</b>	3CPM442 <b>8</b>	BHLW1-10 <b>24</b>	BQL360NA 61
2SL500PCO <b>50</b>	48INT125B <b>25</b>	BHLW2-10 <b>24</b>	BQL370 <b>60</b>
2SL502NV <b>51</b>	52-3125-5 <b>15</b>	BHLW-10 <b>24</b>	BQL390 <b>60</b>
2SL502NVE <b>51</b>	52-3125-6 <b>15</b>	BJ2125 <b>63</b>	BQL2100 <b>60</b>
2SL502VE <b>51</b>	816INT125B <b>25</b>	BJ2150 <b>63</b>	BQL2125 <b>60</b>
2SL602NV <b>51</b>	1224INT125B <b>25</b>	BJ2175 <b>63</b>	BQL2135 <b>60</b>
2SL602NVE <b>51</b>	1624INT125B <b>25</b>	BJ2200 <b>63</b>	BQL3100 <b>60</b>
2SL602VE <b>51</b>	2024INT125B <b>25</b>	BJ3125 <b>63</b>	BQLT15 <b>60</b>
2SL702NV <b>51</b>	2424INT125B <b>25</b>	BJ3150 <b>63</b>	BQLT20 <b>60</b>
2SL702NVE <b>51</b>	4112 <b>59</b>	BJ3175 <b>63</b>	BQLT30 <b>60</b>
2SL702VE <b>51</b>	4116 <b>59</b>	BJ3200 <b>63</b>	BQLT15215 <b>60</b>
3BRS225 <b>15</b>	4120 <b>59</b>	BP2 <b>18</b>	BQLT15220 <b>60</b>
3BRS400 <b>15</b>	4208 <b>59</b>	BP4 <b>18</b>	BQLT15225 <b>60</b>
3CBL118 <b>39</b>	4212 <b>59</b>	BP16 <b>18</b>	BQLT15230 <b>60</b>
3CBL118CU <b>40</b>	4216 <b>59</b>	BP18 <b>18</b>	BQLT15240 <b>60</b>
3CBL130 <b>39</b>	4220 <b>59</b>	BP21 <b>18</b>	BQLT215215 <b>60</b>
3CBL130CU <b>40</b>	4312 <b>59</b>	BP23 <b>18</b>	BQLT215230 <b>60</b>
3CBL142 <b>39</b>	BAB1010 <b>41</b>	BP24 <b>18</b>	BQLT215240 <b>60</b>
3CBL142CU <b>40</b>	BAB1015 <b>41</b>	BP27 <b>18</b>	BQLT220220 <b>60</b>
3CBL218 <b>39</b>	BAB1015D <b>41</b>	BP31 <b>18</b>	BR115 <b>17</b>
3CBL230 <b>39</b>	BAB1020 <b>41</b>	BP32 <b>18</b>	BR115E <b>21</b>
3CBL230CU <b>40</b>	BAB1020D <b>41</b>	BP41 <b>18</b>	BR120 <b>17</b>
3CBL242 <b>39</b>	BAB1025 <b>41</b>	BP54 <b>18</b>	BR120E <b>21</b>
3CBL242CU <b>40</b>	BAB1030 <b>41</b>	BP3110C <b>15</b>	BR125 <b>17</b>
3CBM118 <b>37</b>	BAB1040 <b>41</b>	BQHT-10 <b>24</b>	BR125E <b>21</b>
3CBM118CU <b>38</b>	BAB1050 <b>41</b>	BQL-10 <b>44</b>	BR130 <b>17</b>
3CBM130 <b>37</b>	BAB1060 <b>41</b>	BQL15 <b>60</b>	BR130E <b>21</b>
3CBM130CU <b>38</b>	BAB1070 <b>41</b>	BQL20 <b>60</b>	BR135 <b>17</b>
3CBM142 <b>37</b>	BAB2015 <b>41</b>	BQL25 <b>60</b>	BR135E <b>21</b>
3CBM142CU <b>38</b>	BAB2020 <b>41</b>	BQL30 <b>60</b>	BR140 <b>17</b>
3CBM218 <b>37</b>	BAB2030 <b>41</b>	BQL40 <b>60</b>	BR140E <b>21</b>
3CBM230 <b>37</b>	BAB2040 <b>41</b>	BQL50 <b>60</b>	BR150 <b>17</b>
3CBM230CU <b>38</b>	BAB2050 <b>41</b>	BQL60 <b>60</b>	BR150E <b>21</b>
3CBM242 <b>37</b>	BAB2060 <b>41</b>	BQL215 <b>60</b>	BR160 <b>17</b>
3CBSF100 <b>44</b>	BAB2070 <b>41</b>	BQL220 <b>60</b>	BR160E <b>21</b>
3CBSF225 <b>44</b>	BAB2090 <b>41</b>	BQL225 <b>60</b>	BR170 <b>17</b>

BR170E <b>21</b>	BR390E <b>21</b>	BRH270 <b>17</b>	BRN120AFC <b>19</b>
BR215 <b>17</b>	BR2100 <b>17</b>	BRH270E <b>21</b>	BRN120DFC <b>19</b>
BR215E <b>21</b>	BR2100E <b>21</b>	BRH280 <b>17</b>	BRN120EP <b>20</b>
BR220 <b>17</b>	BR2100NA 22	BRH280E <b>21</b>	BRN120GFC 20
BR220E <b>21</b>	BR2125 <b>17</b>	BRH290 <b>17</b>	BRN125EP <b>20</b>
BR225 <b>17</b>	BR3100 <b>17</b>	BRH290E <b>21</b>	BRN125GFC <b>20</b>
BR225E <b>21</b>	BR3100E <b>21</b>	BRH315 <b>17</b>	BRN130EP <b>20</b>
BR230 <b>17</b>	BRCAFLOFF 24	BRH315E <b>21</b>	BRN130GFC <b>20</b>
BR230E <b>21</b>	BRDL1-10 <b>24</b> , <b>44</b>	BRH320 <b>17</b>	BRP115AFC <b>19</b>
BR235 <b>17</b>	BRF115 <b>19</b>	BRH320E <b>21</b>	BRP115DFC <b>19</b>
BR235E <b>21</b>	BRF120 <b>19</b>	BRH325 <b>17</b>	BRP120AFC <b>19</b>
BR240 <b>17</b>	BRFP <b>15</b> , <b>44</b> , <b>58</b>	BRH325E <b>21</b>	BRP120DFC <b>19</b>
BR240E <b>21</b>	BRH115 <b>17</b>	BRH330 <b>17</b>	BRQLW-10 <b>24</b>
BR245 <b>17</b>	BRH115E <b>21</b>	BRH330E <b>21</b>	BRS225 <b>15</b>
BR245E <b>21</b>	BRH120 <b>17</b>	BRH335 <b>17</b>	BRS400 <b>15</b>
BR250 <b>17</b>	BRH120E <b>21</b>	BRH335E <b>21</b>	BRSF125 <b>15</b>
BR250E <b>21</b>	BRH125 <b>17</b>	BRH340 <b>17</b>	BRSURGE 48
BR250NA <b>22</b>	BRH125E <b>21</b>	BRH340E <b>21</b>	CBL118 <b>39</b>
BR260 <b>17</b>	BRH130 <b>17</b>	BRH345 <b>17</b>	CBL118CU <b>40</b>
BR260E <b>21</b>	BRH130E <b>21</b>	BRH345E <b>21</b>	CBL130 <b>39</b> CBL130CU <b>40</b>
BR260NA <b>22</b>	BRH135 <b>17</b>	BRH350 <b>17</b>	CBL130C0 <b>40</b> CBL142 <b>39</b>
BR270 <b>17</b>	BRH135E <b>21</b>	BRH350E <b>21</b>	CBL142 <b>39</b> CBL142CU <b>40</b>
BR270E <b>21</b> BR280 <b>17</b>	BRH140 <b>17</b> BRH140E <b>21</b>	BRH360 <b>17</b> BRH360E <b>21</b>	CBL142CO <b>40</b> CBL218 <b>39</b>
BR280E <b>21</b>	BRH145 <b>17</b>	BRH370 <b>17</b>	CBL218 <b>39</b> CBL218CU <b>40</b>
BR290 <b>17</b>	BRH145E <b>21</b>	BRH370E <b>21</b>	CBL230 <b>39</b>
BR290E <b>21</b>	BRH150 <b>17</b>	BRH380 <b>17</b>	CBL230CU <b>40</b>
BR315 <b>17</b>	BRH150E <b>21</b>	BRH380E <b>21</b>	CBL230C0 <b>40</b>
BR315E <b>21</b>	BRH160 <b>17</b>	BRH390 <b>17</b>	CBL242 <b>39</b> CBL242CU <b>40</b>
BR320 <b>17</b>	BRH160E <b>21</b>	BRH390E <b>21</b>	CBM118 <b>37</b>
BR320E <b>21</b>	BRH170 <b>17</b>	BRH2100 <b>17</b>	CBM118CU <b>38</b>
BR325 <b>17</b>	BRH170E <b>21</b>	BRH2100E <b>21</b>	CBM130 <b>37</b>
BR325E <b>21</b>	BRH215 <b>17</b>	BRH3100 <b>17</b>	CBM130CU <b>38</b>
BR330 <b>17</b>	BRH215E <b>21</b>	BRH3100E <b>21</b>	CBM142 <b>37</b>
BR330E <b>21</b>	BRH220 <b>17</b>	BRHN115AF <b>19</b>	CBM142CU <b>38</b>
BR335 <b>17</b>	BRH220E <b>21</b>	BRHN115GF <b>20</b>	CBM218 <b>37</b>
BR335E <b>21</b>	BRH225 <b>17</b>	BRHN120AF <b>19</b>	CBM218CU <b>38</b>
BR340 <b>17</b>	BRH225E <b>21</b>	BRHN120GF <b>20</b>	CBM230 <b>37</b>
BR340E <b>21</b>	BRH230 <b>17</b>	BRHN125GF <b>20</b>	CBM230CU <b>38</b>
BR345 <b>17</b>	BRH230E <b>21</b>	BRHN130GF <b>20</b>	CBM242 <b>37</b>
BR345E <b>21</b>	BRH235 <b>17</b>	BRL215CAF <b>19</b>	CBRPL112 <b>10</b>
BR350 <b>17</b>	BRH235E <b>21</b>	BRL220CAF <b>19</b>	CBRPL112G3 <b>46</b>
BR350E <b>21</b>	BRH240 <b>17</b>	BRLAFGFLOFF <b>24</b>	CBRPL112G6 <b>46</b>
BR360 <b>17</b>	BRH240E <b>21</b>	BRLW1-10 <b>24</b>	CBRPL116 <b>10</b>
BR360E <b>21</b>	BRH245 <b>17</b>	BRLW2-10 <b>24</b>	CBRPL120 <b>10</b>
BR370 <b>17</b>	BRH245E <b>21</b>	BRLW-10 <b>24</b>	CBRPL120G6 <b>46</b>
BR370E <b>21</b>	BRH250 <b>17</b>	BRN115AFC <b>19</b>	CBRPL130 <b>10</b>
BR380 <b>17</b>	BRH250E <b>21</b>	BRN115DFC <b>19</b>	CBRPL130G6 <b>46</b>
BR380E <b>21</b>	BRH260 <b>17</b>	BRN115EP <b>20</b>	CBRPL220 <b>10</b>
BR390 <b>17</b>	BRH260E <b>21</b>	BRN115GFC <b>20</b>	CBRPL240 <b>10</b>
			••

CBRPM112 6	CH215EPD <b>34</b>	CHF250 <b>31</b>	CHP280 <b>32</b>
CBRPM116 6	CH215GFT <b>34</b>	CHFAFGF115 33	CHP290 <b>32</b>
CBRPM116Z <b>6</b>	CH220CAF <b>33</b>	CHFAFGF115PN 33	CHP310 <b>32</b>
CBRPM120 6	CH220EPD <b>34</b>	CHFAFGF120 33	CHP315 <b>32</b>
CBRPM130 6	CH220GFT <b>34</b>	CHFAFGF120PN 33	CHP320 <b>32</b>
CBRPM130Z 6	CH225GFT <b>34</b>	CHFAFGFLOFF 36	CHP325 <b>32</b>
CBRPM140 6	CH230EPD <b>34</b>	CHFCAF115 33	CHP330 <b>32</b>
CBRPM140Z 6	CH230GFT <b>34</b>	CHFCAF115PN 33	CHP335 <b>32</b>
CBRPM216 6	CH235GFT <b>34</b>	CHFCAF120 33	CHP340 <b>32</b>
CBRPM220 6	CH240EPD <b>34</b>	CHFCAF120PN 33	CHP345 <b>32</b>
CBRPM230 6	CH240GFT <b>34</b>	CHFEP115 <b>34</b>	CHP350 <b>32</b>
CBRPM236GEN <b>45</b> , <b>46</b>	CH245GFT <b>34</b>	CHFEP120 <b>34</b>	CHP360 <b>32</b>
CBRPM240 6	CH250EPD <b>34</b>	CHFEP125 <b>34</b>	CHP370 <b>32</b>
CBRPM260 6	CH250GFT <b>34</b>	CHFEP130 <b>34</b>	CHP2100 <b>32</b>
CBRPM1520 <b>6</b>	CH250SUR <b>48</b>	CHFGFT115 34	CHP2125 <b>32</b>
CBRPM1530 <b>6</b>	CH260 <b>31</b>	CHFGFT115PN 34	CHP3100 <b>32</b>
CBRPM1540 <b>6</b>	CH260EPD <b>34</b>	CHFGFT120 <b>34</b>	CHPL 36
CBSF100 <b>44</b>	CH260GFT <b>34</b>	CHFGFT120PN 34	CHPLGF 36
CBSF225 <b>44</b>	CH270 <b>31</b>	CHFGFT125 <b>34</b>	CHRLS 36
CC3100 <b>23</b>	CH280 <b>31</b>	CHFGFT130 <b>34</b>	CHSF2125 <b>36</b>
CC3125 <b>23</b>	CH290 <b>31</b>	CHFGFT130PN 34	CHSPALARM 47
CC3150 <b>23</b>	CH310 <b>31</b>	CHFP 36	CHSPCABLE 49
CC3200 <b>23</b>	CH315 <b>31</b>	CHHT <b>36</b>	CHSPFMKIT 49
CCHPL124 <b>30</b>	CH320 <b>31</b>	CHLO 36	CHSPT2MICRO 49
CCHPL232 <b>30</b>	CH325 <b>31</b>	CHNS 36	CHSPT2ULTRA 49
CCHPM124 <b>30</b>	CH330 <b>31</b>	CHNT1515 <b>31</b>	CHSPT22PACK 49
CCHPM132 <b>30</b>	CH335 <b>31</b>	CHNT1520 <b>31</b>	CHT1515 <b>31</b>
CCHPM132Z <b>30</b>	CH340 <b>31</b>	CHNT2020 <b>31</b>	CHT1520 <b>31</b>
CCHPM142 <b>30</b>	CH345 <b>31</b>	CHP110 <b>32</b>	CHT2020 <b>31</b>
CCHPM142Z <b>30</b>	CH350 <b>31</b>	CHP115 <b>32</b>	CHWPS2040D <b>64</b>
CCHPM242 <b>30</b>	CH360 <b>31</b>	CHP120 <b>32</b>	CHWPS2040DL <b>64</b>
CCHPM260 <b>30</b>	CH370 <b>31</b>	CHP125 <b>32</b>	CHWPS2040DP <b>64</b>
CCL300 <b>24</b>	CH380 <b>31</b>	CHP130 <b>32</b>	CHWPS3050D <b>64</b>
CCPL 24	CH390 <b>31</b>	CHP135 <b>32</b>	CHWPS3050DL <b>64</b>
CCPL102 <b>10</b>	CH3100 <b>31</b>	CHP140 <b>32</b>	CHWPS4060D <b>64</b>
CCPL104 <b>10</b>	CHF115 <b>31</b>	CHP145 <b>32</b>	CPL072 <b>14</b>
CCPL108 <b>10</b>	CHF120 <b>31</b>	CHP150 <b>32</b>	CPL072FGP <b>14</b>
CH6L125R <b>30</b>	CHF125 <b>31</b>	CHP160 <b>32</b>	CPL072R <b>14</b>
CH9FL <b>15</b>	CHF130 <b>31</b>	CHP170 <b>32</b>	CPL072RGP <b>14</b>
CH30SPAST 47	CHF135 <b>31</b>	CHP210 <b>32</b>	CPL072SGP <b>14</b>
CH40SPAST 47	CHF140 <b>31</b>	CHP215 <b>32</b>	CPL400KIT <b>15</b>
CH50SPAST 47	CHF145 <b>31</b>	CHP220 <b>32</b>	CPL442 <b>10</b>
CH60SPAST 47	CHF150 <b>31</b>	CHP225 <b>32</b>	CPM116COV <b>15</b>
CH115AF <b>33</b>	CHF215 <b>31</b>	CHP230 <b>32</b>	CPM120COV <b>15</b>
CH115AFPN <b>33</b>	CHF220 <b>31</b>	CHP235 <b>32</b>	CPM342 <b>6</b>
CH115EPD <b>34</b>	CHF225 <b>31</b>	CHP240 <b>32</b>	CPM400KIT <b>15</b>
CH115GF <b>34</b>	CHF230 <b>31</b>	CHP245 <b>32</b>	CPM442 <b>6</b>
CH160 <b>31</b>	CHF235 <b>31</b>	CHP250 <b>32</b>	CPM1520 <b>6</b>
CH170 <b>31</b>	CHF240 <b>31</b>	CHP260 <b>32</b>	CPM1530 <b>6</b>
CH215CAF <b>33</b>	CHF245 <b>31</b>	CHP270 <b>32</b>	CPM1540 <b>6</b>

CQLP8100 <b>58</b> , <b>59</b>	GFTCB230 <b>20</b>	NHP20-1231 <b>59</b>	QB1030GF <b>43</b>
CQLP12100 <b>58</b> , <b>59</b>	GFTCB240 <b>20</b>	NL20 <b>15</b>	QBGFEP2015 <b>43</b>
CSABP4683B <b>58</b>	GFTCB250 <b>20</b>	NL30 <b>15</b>	QBGFEP2020 <b>43</b>
CSABP4734B <b>58</b>	GFTCB260 <b>20</b>	NL300 <b>15</b>	QBGFEP2025 <b>43</b>
CSR2100N <b>35</b>	GFTCBH215 <b>20</b>	NSP42 <b>15</b>	QBGFEP2030 <b>43</b>
CSR2125N <b>23</b> , <b>35</b>	GFTCBH220 <b>20</b>	P48G11S03CUB <b>56</b>	QBGFT1040 <b>43</b>
CSR2150N <b>23</b> , <b>35</b>	GFTCBH225 <b>20</b>	P48G11S03P <b>55</b>	QBGFT2015 <b>43</b>
CSR2200N <b>23</b> , <b>35</b>	GFTCBH230 <b>20</b>	P48G11S05CUB <b>56</b>	QBGFT2020 <b>43</b>
CVRSCRW 15	GFXB115B2 <b>22</b>	P48G11S05P <b>55</b>	QBGFT2030 <b>43</b>
DIRCARD42 44	GFXB120B2 <b>22</b>	P48G11S07CUB <b>56</b>	QBGFT2040 <b>43</b>
DIRSLEEVE 44	GFXB125B2 <b>22</b>	P48G11S07P <b>55</b>	QBGFT2050 <b>43</b>
DNBA1515 <b>42</b>	GFXB130B2 <b>22</b>	P48G11S10CUB <b>56</b>	QBH15 <b>62</b>
DNBA2020 <b>42</b>	HBQL15 <b>60</b>	P48G11S10P <b>55</b>	QBH20 <b>62</b>
DNBA3030 <b>42</b>	HBQL20 <b>60</b>	P48G11S15CUB <b>56</b>	QBH25 <b>62</b>
DNPL1515 <b>18</b>	HBQL25 <b>60</b>	P48G11S15P <b>55</b>	QBH30 <b>62</b>
DNPL1515E <b>21</b>	HBQL30 <b>60</b>	P48G11S25CUB <b>56</b>	QBH40 <b>62</b>
DNPL1520 <b>18</b>	HBQL40 <b>60</b>	P48G11S25P <b>55</b>	QBH50 <b>62</b>
DNPL1520E <b>21</b>	HBQL50 <b>60</b>	P48G28T15CUB <b>56</b>	QBH60 <b>62</b>
DNPL1530 <b>18</b>	HBQL60 <b>60</b>	P48G28T15P <b>55</b>	QBH215 <b>62</b>
DNPL2020 <b>18</b>	HBQL315 <b>60</b>	P48G28T21CUB <b>56</b>	QBH220 <b>62</b>
DNPL2020E <b>21</b>	HBQL330 <b>60</b>	P48G28T21P <b>55</b>	QBH225 <b>62</b>
DNPL151515 <b>18</b>	HBQL350 <b>60</b>	P48G28T30CUB <b>56</b>	QBH230 <b>62</b>
DNPL152015 <b>18</b>	HBQL360 <b>60</b>	P48G28T30P <b>55</b>	QBH240 <b>62</b>
DNPL152515 <b>18</b>	HBQL370 <b>60</b>	P60G11S03CUB <b>56</b>	QBH250 <b>62</b>
DNPL153015 <b>18</b>	HBQL390 <b>60</b>	P60G11S05CUB <b>56</b>	QBH260 <b>62</b>
DNPL154015 <b>18</b>	HBQL3100 <b>60</b>	P60G11S05P <b>55</b>	QBH270 <b>62</b>
DNPL155015 <b>18</b>	HLW1-10 <b>24</b>	P60G11S07CUB <b>56</b>	QBH290 <b>62</b>
DNPL215215 <b>18</b>	ISGRD <b>15</b> , <b>44</b>	P60G11S07P <b>55</b>	QBH1015AFGF <b>42</b>
DNPL215220 <b>18</b>	LCCS 36	P60G11S10CUB <b>56</b>	QBH1015CAF <b>42</b>
DNPL215230 <b>18</b>	MCBL300 <b>24</b>	P60G11S10P <b>55</b>	QBH1015EP <b>43</b>
DNPL215240 <b>18</b>	MCBPL <b>24</b> , <b>36</b>	P60G11S15CUB <b>56</b>	QBH1020AFGF <b>42</b>
DNPL220220 <b>18</b>	NHP4-632 <b>59</b>	P60G11S15P <b>55</b>	QBH1020CAF <b>42</b>
DNPL220230 <b>18</b>	NHP6-30-60 <b>59</b>	P60G11S25CUB <b>56</b>	QBH1020EP <b>43</b>
DS075H1 <b>15</b>	NHP6-60 <b>59</b>	P60G11S25P <b>55</b>	QBH1025EP <b>43</b>
DS100H1 <b>15</b>	NHP6-633 <b>59</b>	P60G28T15CUB <b>56</b>	QBH1030EP <b>43</b>
DS125H1 <b>15</b>	NHP6-636-4 <b>59</b>	P60G28T15P <b>55</b>	QBH2100 <b>62</b>
DS150H1 <b>15</b>	NHP8-60 <b>59</b>	P60G28T21CUB <b>56</b>	QBH2125 <b>62</b>
DS200H1 <b>15</b>	NHP8-635-3 <b>59</b>	P60G28T21P <b>55</b>	QBHGFEP2015 <b>43</b>
DS200H2 <b>15</b> , <b>52</b> , <b>53</b>	NHP10-0401-4 <b>59</b>	P60G28T30CUB <b>56</b>	QBHGFEP2020 <b>43</b>
DS250H2 <b>15</b> , <b>52</b> , <b>53</b>	NHP10-0601-2 <b>59</b>	P60G28T30P <b>55</b>	QBHGFEP2025 <b>43</b>
DS300H2 <b>15</b> , <b>52</b> , <b>53</b>	NHP10-0611 <b>59</b>	QB1015AFGF <b>42</b>	QBHGFEP2030 <b>43</b>
GFEP215 <b>20</b>	NHP10-636-3 <b>59</b>	QB1015CAF <b>42</b>	QBHW1015 <b>41</b>
GFEP220 <b>20</b>	NHP10-0801 <b>59</b>	QB1015EP <b>43</b>	QBHW1020 <b>41</b>
GFEP225 <b>20</b>	NHP12-60 <b>59</b>	QB1015GF <b>43</b>	QBHW1030 <b>41</b>
GFEP230 <b>20</b>	NHP12-633 <b>59</b>	QB1020AFGF <b>42</b>	QBHW1040 <b>41</b>
GFEP240 <b>20</b>	NHP12-0811 <b>59</b>	QB1020CAF <b>42</b>	QBHW1050 <b>41</b>
GFEP250 <b>20</b>	NHP12B-1000-2 <b>59</b>	QB1020EP <b>43</b>	QBHW1060 <b>41</b>
GFTCB215 <b>20</b>	NHP14-0621-2 <b>59</b>	QB1020GF <b>43</b>	QBHW1070 <b>41</b>
GFTCB220 <b>20</b>	NHP14-0801-4 <b>59</b>	QB1025EP <b>43</b>	QBHW2015 <b>41</b>
GFTCB225 <b>20</b>	NHP20-0821-6 <b>59</b>	QB1030EP <b>43</b>	QBHW2020 <b>41</b>

QBHW2030 <b>41</b>	RCPM108M <b>52</b>
QBHW2040 <b>41</b>	RCPM112 <b>7</b>
QBHW2050 <b>41</b>	RCPM120 <b>7</b>
QBHW2060 <b>41</b>	RCPM130 <b>7</b>
QBHW2070 <b>41</b>	RCPM208M <b>52</b>
QBHW2090 <b>41</b>	RCPM220 <b>7</b>
QBHW2100 <b>41</b>	RCPM230 <b>7</b>
QBHW2125 <b>41</b>	RCPM240 <b>7</b>
QBHW3015 <b>41</b>	RCPM1530 <b>7</b>
QBHW3020 <b>41</b>	RH75P <b>15</b>
QBHW3030 <b>41</b>	RH100P <b>15</b>
QBHW3040 <b>41</b>	RH125P <b>15</b>
QBHW3050 <b>41</b>	SPC61 <b>15</b>
QBHW3060 <b>41</b>	SPCWH 15
QBHW3070 <b>41</b>	TDL <b>15</b> , <b>36</b> , <b>44</b>
QBHW3090 <b>41</b>	THOW-10 <b>24</b>
QBHW3100 <b>41</b>	THS1 <b>24</b>
QL1NPL <b>44</b>	
QL23NPL <b>44</b>	
QL123PL <b>44</b>	
QLPT14D <b>59</b>	
QLPT16AD <b>59</b>	
QLPT16D <b>59</b>	
QLPT19D <b>59</b>	
QLPT20AD <b>59</b>	
QLPT20D <b>59</b>	
QLPT22AD <b>59</b>	
QLPT24D <b>59</b>	
QLPT24LD <b>59</b>	
R3CCPL103 <b>13</b>	
R3CPL112 <b>13</b>	
R3CPL130 <b>13</b>	
R3CPL136 <b>13</b>	
R3CPL230 <b>13</b>	
R3CPL242 <b>13</b>	
R3CPM112 <b>9</b>	
R3CPM130 <b>9</b>	
R3CPM230 <b>9</b>	
RCCHL102 <b>30</b>	
RCCPL102 <b>11</b>	
RCCPL104 <b>11</b>	
RCCPL108 <b>11</b>	
RCPL112 <b>11</b>	
RCPL120 <b>11</b>	
RCPL130 <b>11</b>	
RCPL220 <b>11</b>	
RCPL240 <b>11</b>	
RCPM1GF6H <b>53</b>	
RCPM1GF10 <b>53</b>	
RCPM2GF6H <b>53</b>	
DODI 400540 ==	

RCPM2GF10 **53** 

#### Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

Canadian Operations 5050 Mainway Burlington, ON L7L 5Z1 Canada EatonCanada.ca

© 2019 Eaton All Rights Reserved Printed in Canada Publication No. CA003011EN March 2019

