NEW

Hand Tools

Greenlee is proud to introduce a brand new line of professional hand tools designed with you, our customer, in mind. This new line of hand tools is a natural extension to Greenlee's existing product lines. The comprehensive assortment features custom-designed high-quality pliers, saws, screwdrivers, wrenches, insulated drivers, tool bags, accessories, tool kits and more - all bearing the Greenlee name. We believe you'll be proud to claim Greenlee hand tools as your preferred brand.





PLIERS

High Leverage Side-Cutting Pliers



- · Rugged riveted construction for smooth precise action.
- Custom grip allows area for user identification.
- Slip-proof, ergonomic molded grips for increased comfort and reduced user fatigue.
- · Wider grip design provides larger load bearing area.
- Location of handle ridge allows for user to "choke up" for greater control.
- High leverage pliers design and diamond-serrated jaws for optimum cutting and gripping performance.
- Forged from chrome vanadium steel for greater durability and strength.
- Precision-machined and induction-hardened blades strengthen cutters and provide consistent performance.
- · Effectively cuts hardened wire, ACSR, bolts, screws and nails.
- Through-hardened steel for longer life.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION	
0151-08M 0151-09M 0151-09M-CP	54701 54702 95925	High Leverage Side	-cutting Pliers 8" molded grip -cutting Pliers 9" molded grip cutting Pliers 9" Counter Pack (Qty 5)
SPECIFICATIONS		8"	9"
Overall Length		8-1/2" (21.6 cm)	9-3/8" (23.8 cm)
Weight		.87 lbs. (.04 kg)	1.13 lbs. (.51 kg)

Diagonal Cutting Pliers



- Rugged riveted construction for smooth precise action.
- Custom grip allows area for user identification.
- Flared handles for added comfort and leverage.
- Wider grip design provides larger load bearing area for user comfort.
- Forged from chrome vanadium steel for greater durability and strength
- Precision-machined and induction-hardened blades strengthen cutters and provide consistent performance.
- Effectively cuts most hardened wire, ACSR, bolts, screws and nails.
- Through-hardened steel for longer life.
- · Dual cutting edges for optimum cutting performance
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DES	CRIPTION		
0251-05M	54736	Diag	onal Cutting Plier	s 5" Mini molded	grip
0251-06M	54737	Diagonal Cutting Pliers 6" molded grip			
0251-07M	54738	Higl	n Leverage Diagor	nal Cutting Pliers	7" molded grip
0251-08M	54739	Higl	n Leverage Diagor	nal Cutting Pliers	8" molded grip
0251-08M-CP	95926	·	n Leverage Diagor nter Pack (Qty 5)	nal Cutting Pliers	8" molded grip
0251-08AM	54740	High	Leverage Diagonal	Cutting Pliers 8" ar	ngled molded grip
SPECIFICATIONS	5"		6"	7"	8"
Overall Length	5-1/2" (14.0) cm)	6-1/8" (15.5 cm)	7" (17.8 cm)	8-3/4" (22.2 cm)
Weight	.28 lbs. (.1	3 kg)	.35 lbs. (.16 kg)	.57 lbs. (.26 kg)	.85 lbs. (.39 kg)

Long Nose Pliers/Side Cutting



- Rugged riveted construction for smooth precise action.
- · Custom grip allows area for user identification.
- Flared handles for added comfort and leverage.
- · Wider grip design provides larger load bearing area.
- Forged from chrome vanadium steel for greater durability and strength.
- Effectively cuts most hardened wire, ACSR, bolts, screws and nails.
- Diamond-serrated jaws and hardened cutting edges for optimum cutting and gripping performance.
- Through-hardened steel for longer life.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION	N	
0351-06M	54717	Long Nose P	liers/Side Cutting 6" mo	olded grip
0351-07M	54718	Long Nose P	liers/Side Cutting 7" mo	olded grip
0351-08M	54719	Long Nose P	liers/Side Cutting 8" mo	olded grip
SPECIFICATION	ONS	6"	7"	8"
Overall Lengt	th 6-5/	8" (16.8 cm)	7-1/8" (18.1 cm)	8-9/16" (21.7 cm)
Weight	.27	lbs. (.12 kg)	.30 lbs. (.14 kg)	.64 lbs. (.29 kg)

Pump Pliers



- Custom grip allows area for user identification.
- Slip-proof, ergonomic molded grip for increased comfort and reduced user fatique.
- · Wider grip design provides larger load bearing area.
- Precision-machined and through-hardened for consistent performance and longer life.
- Right-angled teeth for gripping in both directions.
- Riveted process ensures joint integrity.
- · Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

LIDO NO

GAI. NO.	UPC NO.	DESCRIPTION	
0451-10M	54709	Pump Pliers 10" molded	grip
0451-10M-CP	95927	Pump Pliers 10" molded	grip Counter Pack (Qty 5)
0451-12M	54744	Pump Pliers 12" molded grip	
SPECIFICATIONS	,	10"	12"
Overall Length		10" (25.4 cm)	12" (30.5 cm)
Overall Length Weight	-	10" (25.4 cm) .83 lbs. (.38 kg)	12" (30.5 cm) 1.29 lbs. (.59 kg)
•	oves	,	,

- Double dipped grips for added comfort and slip resistance.
 - Precision-machined and through-hardened for consistent performance and longer life.
- · Right-angled teeth for gripping in both directions.
- · Riveted process ensures joint integrity.
- Lifetime limited warranty.
- Note: This is not an insulated tool.


CAT. NO.	UPC NO.	DESCRIPTION
0451-16D	54707	Pump Pliers 16" dipped grip
SPECIFICATIONS		16"
Overall Lengt	h	16" (40.6 cm)
Overall Length Weight	h	16" (40.6 cm) 3 lbs. (1.4 kg)
Ū		, ,





CUTTING AND STRIPPING TOOLS

Pro Wire Strippers



- Strips the outer jacket off both solid and stranded wire.
- Machined stripping stations with a positive stop provide precise stripping diameters.
- Ergonomically designed, extra-long cushioned handles add superior comfort and reduce hand fatigue.
- Long curved cutter blades reduce force required by 25% and can cut NM in a single cut.
- Lock tab protects cutting edges during storage.
- Pliers nose for working with small nuts and pulling wire.
- · Hole in jaws for looping wires.
- Opening stop prevents spring from disengaging.
- Cuts screws.
- Note: These are not insulated tools.

CAT. NO.	UPC NO.	DESCRIPTION
1950	06852	Pro Stripper 10-18 AWG
1951	06853	Pro Wire Stripper 22-32 AWG
1955	06857	Pro Plus Wire Stripper, 10-18 AWG
1956	10300	Pro Plus Stripper 8-16 AWG

SPECIFICATIONS

Strips	1950 & 1955 – 10-18 AWG solid, 12-20 AWG stranded; 1951 – 22-32 AWG solid, 20-30 AWG stranded;
	1956 – 6-14 AWG solid, 8-16 AWG stranded
Cuts	#6-32 and #8-32 screws
Overall Length	1950 & 1951 – 7-1/4" (18.4 cm)
	1955 & 1956 – 7-3/8" (18.7 cm)

Wire Stripper/Cutters



CAT. NO.	UPC NO.	DESCRIPTION
1916	31891	20-10 AWG (0.8 to 2.6 mm dia.) Solid Wire
1917	31890	26-16 AWG (0.4 to 1.3 mm dia.) Solid Wire
1918	31889	30-22 AWG (0.25 to 0.64 mm dia.) Solid Wire

- Precision ground blades ensure consistent stripping and cutting.
- · Heat-treated for long life.
- Cushioned-grip vinyl handle for comfortable use.
- Serrated nose grip for wire pulling and straightening.
- Stamped from high-carbon tool steel.
- Pivot joints have hardened steel bushings.
- Rust-resistant black oxide finish.
- · Note: This is not an insulated tool.

SPECIFICATIONS

Capacity	PVC or THHN insulation 1916 - 20-10 AWG (0.5-6 mm²) 1917 - 26-16 AWG (0.25-1.5 mm²) 1918 - 30-22 AWG (0.2534 mm²)
	1910 - 30-22 AWG (0.2334 IIIII-)
Weight	.2 lb. (.10 kg) All Models

V-Notch Wire Stripper/Cutter



SPECIFICATIONS	
Capacity	30 - 10 AWG (.25 - 6 mm²) with PVC or THHN insulation
Weight	16 lh (07 kg)

- Stamped from high-carbon tool steel with black oxide finish.
- · Pivot joints have hardened-steel bushings.
- Vinyl cushioned grip.
- · Precision-ground blades for consistent stripping and cutting.
- · Adjustable settings for various wire size.
- Heat treated for long life.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
1913	31894	The Terminators V-Notch Wire Stripper/Cutter
1914	31893	The Terminators V-Notch Wire Stripper/Cutter with Spring and Lock function



Production grade wire stripper strips insulation from most smaller gauge wire.

- Strips up to 7/8" (22.2 mm) length.
- Strips PVC and THHN insulation.
- For use with solid and stranded wire.
- · Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
1935	37600	Automatic Wire Stripper
ODFOLEIO ATIONIO		

SPECIFICATIONS

Capacity	20 - 10 AWG (.5 mm ² - 6 mm ²) with PVC or THHN insulation	
Weight	.7 lb. (.30 kg)	

Kwik Stripper® Wire Stripper



- 28-10 AWG (.08-6mm²) stripping capacity.
- 12 AWG (4 mm²) solid, 10 AWG (6 mm²) stranded capacity.
- Strips and cuts flat and round cable.
- · Self-adjusts to different wire gauges.
- Laminated steel blades minimize the risk of nicking conductors.
- Front entry jaws have an adjustable strip length guide.
- · Lightweight reinforced nylon is chemical and corrosion resistant.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
45000	45000	Kwik Stripper Wire Stripper

Pro Wire Stripper for NM Cable



CAT. NO.	UPC NO.	DESCRIPTION
1960	06854	Pro Stripper 12/2 & 14/2

- · Pliers' nose for working with small nuts and pulling wire.
- Machined stripping stations with a positive stop provide precise stripping diameters.
- Long curved cutter blades reduce force required by 25% and can cut NM in single cut.
- · Hole in jaws for looping wires.
- Extra-long cushioned handles add comfort and reduce hand fatigue.
- Opening stop prevents spring from disengaging.
- · Lock tab protects cutting edges during storage.
- Cuts #6-32 & #8-32 screws.
- · Note: This is not an insulated tool.

SPECIFICATIONS

Removes	NM-B outer jacket
Strips	#12 and #14 AWG solid
Cuts	#6-32 and #8-32 screws
Overall Length	7-3/4" (19.7 cm)

NM Cable Ripper



- Slits outer jacket of Romex® 10/2, 12/2, 14/2 and other non-metallic (NM) sheathed cable.
- Wire gauge on handle for identifying #6 to #14 AWG.
- · Corrosion-resistant zinc plating.
- · Side-entry design for end or mid-run slitting of jacket.

CAT. NO.	UPC NO.	DESCRIPTION
0252-11	56300	NM Cable Ripper
SPECIFICATION	ONS	

Overall Length	3-5/8" (9.2 cm)
Weight	.06 lbs. (.03 kg)

Stripping/Crimping Combination Tool

GREENLEE



	ALC: NO STATE OF THE PARTY OF T
	Mary Alla
W 2 1-1	The state of the s
MALE WITHOUT BUT AS IN THE	0 6 2
Control of the late of the lat	landar .
100 PM	
The state of the s	NEW BUILDING
	MOTATION
	THE DESIGNATION OF THE PARTY OF

 Pliers' r 	nose avoids	having to	switch too	ls for	arippina	tasks
-------------------------------	-------------	-----------	------------	--------	----------	-------


- Extra-narrow nose for getting into tight boxes.
- Machined stripping stations with a positive stop provide precise stripping diameters.
- · Wire looping holes in jaw.
- · Long, curved cutter blades reduce force required by 25% and can cut NM in single cut.
- Screw cutting stations are collapsed around the pivot 20% less force is required.
- · Smooth, rounded pivot bolt won't catch in tool pouch or on other tools.
- Comfortable, cushioned grips.
- · Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
1927	06851	Stripping/Crimping Combination Tool

SPECIFICATIONS

Strips	10-22 AWG solid and stranded
Crimps	10-22 AWG insulated and non-insulated terminals
Cuts	#4-40, #5-40, #6-32, #8-32, #10-24 and #10-32 screws
Overall Length	8-1/8" (20.6 cm)

Crimping/Stripping Combination Tool



•	op-mont	Cutter 101	Shirbhind	naru-lu-reach	WII 65.


- Narrow nose for getting into tight boxes.
- · Wire looping holes in jaw.
- Screw cutting stations are collapsed around the pivot 20% less force is required.
- Machined stripping stations with a positive stop provide precise stripping diameters.
- Long, curved cutter blades reduce force required by 25% and can cut NM in single cut.
- Smooth, rounded pivot bolt won't catch in tool pouch or on other tools.
- Comfortable, cushioned grips.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
1923	06850	Crimping/Stripping Combination Tool

SPECIFICATIONS

Strips	8-18 AWG solid, 10-22 AWG stranded
Crimps	10-22 AWG insulated and non-insulated terminals
Cuts	#4-40, #6-32, #8-32, #10-24 and #10-32 screws
Overall Length	8-1/2" (21.6 cm)

Combination Tool



CAT. NO.	UPC NO.	DESCRIPTION
1921	31888	The Terminators Combination Tool

- · Crimp, strip and cut wire with a single tool, also cut and re-thread screws.
- · Hardened alloy steel with black oxide finish.
- · Pivot joints have hardened-steel bushings.
- New, softer grips.
- Precision-ground blades for fast, easy and consistent wire stripping and cutting.
- · Note: This is not an insulated tool.

Capacity	PVC or THHN insulation Cut – 22 - 10 AWG (.34 mm² - 6 mm²) Strip – 22 - 10 AWG (.34 mm² - 6 mm²) Crimp – insulated and non insulated, 22 - 10 AWG (.34 mm² - 6 mm²) Terminals and Splices; 7 and 8 mm Ignition Terminals Screws – Cut & Re-thread, 10-24, 10-32, 8-32, 6-32 and 4-40
Length	8-5/8" (22.0 cm)
Weight	.5 lb. (.23 kg)

Cable Cutter



- Easily cuts heavier copper and aluminum cables up to 2/0 (70 mm²).
- Plastic coated, high-leverage handles for easier cuts.
- Heat-treated for long life.
- Made of heavy-duty forged steel.
- Precision ground, shear action, curved cutting blades.
- Rust-resistant black oxide finish.
- Note: This is not an insulated tool.

 CAT. NO. UPC NO. DESCRIPTION

727	31291	Cable Cutter		
SPECIFICA	TIONS	Copper	Aluminum	Comm. Cable
Max Capa	city	2/0 (70 mm²)		
Frequent l	Jse Capacity	#1 AWG (35 mm ²)	2/0 (70 mm ²)	100 pair
Overall Length			9-1/4" (235 mm)	
Weight			1 lb. (.45 kg)	

Utility Knife



- · Over-molded for secure, comfortable grip.
- Retractable three-position blade for safety and convenience.
- · Easy front-loading design provides for quick blade change.
- · Blade storage in pop-up holder.
- Packaged with three heavy-duty patented serrated blades (Cat # 9952-11).
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0652-11 0652-11-CP	54729 95928	Utility Knife with blades Utility Knife with blades Counter Pack (Qty 10)
9952-11		Blades for 0652-11 Utility Knife
SPECIFICATION	NS	
Overall Length	(closed)	6-3/16" (15.7 cm)
Weight		.44 lb. (.20 kg)

Keyhole Saw



- Integrated blade and handle design provides maximum strength.
- Ergonomic handle with non-slip grip.

GRENLES

Overall Length

Weight

- · Hardened steel blade with clog-free teeth.
- Pointed tip easily punches through drywall.

11-5/8" (29.5 mm)

.27 lb. (.12 kg)

- · Blade cuts on both push and pull strokes.
- Hole in handle may be used for lanyard or convenient storage.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
301A	23641	6" Keyhole Saw
SPECIFICA	TIONS	





- 6" blade retracts into the handle for convenience and safety.
- Quickly change blade for added versatility.
- Accepts most 6" (or shorter) standard reciprocating saw blades.
- Ergonomically designed handle allows force to be applied both on the push and pull stroke.
- Built-in blade storage area can hold 2 additional blades.
- Adjustable blade can be used at any length or the 3 hard stops can be used for aggressive sawing.
- Jab blade and a bi-metal blade included.
- Patent-Pending.

CAPACITY Jab Blade

Bimetal Blade

• Note: This is not an insulated tool.

CAT. NO.	UPC NO	D. DESCF	RIPTION
311	13110		stable Saw Set
311-JAB	71945	😘 Jab Bl	ades
SPECIFICA	TIONS		
Overall Ler	ngth:	8-3/8"	21.3 cm (33.0 cm blade extended)
Height:		1-3/4"	4.3 cm
Width:		1-1/8"	2.8 cm
Weight:		.35 lbs.	1.6 kg

Drywall, Ceiling Tile, Wood

Conduit, Metal, PVC, Plastics





- · Over-molded rugged design for heavy-duty use and comfort.
- Fully-adjustable blade tension up to 30,000 psi for longer blade life and faster, accurate cuts.
- · Alternative 45° blade mounting allows for flush cutting.
- · Mounting for most reciprocating saw blades for extra versatility.
- · Handy blade storage in tubular frame.
- Convenient front grip feature for two-handed sawing.
- Complete with bi-metal blade (12"/24 TPI).
- Lifetime limited warranty.

SPECIFICATIONS	
Overall Length	15-3/4" (40.0 cm)
Weight	2.15 lbs. (.98 kg)
Blade Tension	30 KSI

CAT. NO.	UPC NO.	DESCRIPTION
333A	56302	12" Heavy Duty Hacksaw
333-1218	10037	12" (30.5 cm) Bi-metal Blade, 18 teeth per inch
333-1224	10038	12" (30.5 cm) Bi-metal Blade, 24 teeth per inch
333-1232	10039	12" (30.5 cm) Bi-metal Blade, 32 teeth per inch



PVC Saws



- "V" tooth design enables straight cuts on both push and pull saw strokes.
- Blade can be sharpened for extended use.
- Pointed blade nose makes drywall surface penetration easy.
- Ergonomic handle is interchangeable with most popular PVC saw brands.

CAT. NO.	UPC NO.	BLADE LENGTH	DESCRIPTION
322-013	00113	13" (33.0 cm)	PVC Saw
322-018	00114	18" (45.7 cm)	PVC Saw
322-113	00115	13" (33.0 cm)	Blade for 00113
322-118	00116	18" (45.7 cm)	Blade for 00114

SPECIFICATIONS	13"	18"
Overall Length	13-1/2" (34.3 cm)	23-3/4" (60.3 cm)
Weight	.69 lbs. (.31 kg)	.82 lbs. (.37 kg)

PVC Cutter for up to 1"



- Cuts a wide range of PVC conduit, plastic pipe and rubber hose.
- Lightweight, easy to put in tool pouch.
- · Tough nylon handles.
- Replaceable stainless steel blade.

	CAT. NO.	UPC NO.	DESCRIPTION
	861	09861	PVC Cutter for up to 1"
	07995	07995 😗	Blade
	SPECIFICATIONS Capacity Up thr		
			rough 1" PVC

Capacity
Weight

Capacity	Up through 1" PVC
Weight	0.24 lbs. (0.11 kg)

PVC Cutter for up to 1-1/4"



- · Ratchet action for fast, easy cutting.
- · Heat-treated, replaceable steel blade for long cutting life.
- Rugged metal alloy frame for durability.

CAT. NO.	UPC NO.	DESCRIPTION
864 00355	04253 00355	PVC Cutter for up to 1-1/4" Blade Kit
SPECIFICATIONS		
Capacity	Up th	ıru 1-1/4" PVC

PVC Cutter for up to 2"



- · High-leverage compound ratchet action and long handles reduce effort.
- · Heavy-duty metal frame for cutting large diameters.
- Replaceable steel blade may be sharpened.

0.8 lbs. (0.4 kg)

CAT. NO.	UPC NO.	. DESCRIPTION
865	09865	PVC Cutter for up to 2"
07978	07978	(i) Blade

SPECIFICATIONS

Weight

Capacity	Up thru 2" PVC	
Weight	2.5 lbs. (1.1 kg)	

Flex Splitter® MC and Flexible Conduit Cutter



- Cut flexible metal conduit in seconds with a few turns of the crank and an easy twist of the conduit.
- Ample clearance between handle and body for comfortable operation.
- Set conduit size for multiple cuts of the same size conduit. No need to reset.
- · Compact and lightweight. Fits easily in back pocket or tool pouch.
- Set blade adjustment with only a screwdriver.
- Convenient in-handle blade storage holds up to five spare blades.
- Point-of-purchase packaged. Blades point-of-purchase packaged 1 and 5 blades per package.

SP		α	TIO	AIC.
22	н.,	ι.Δ		IIV.

GREENLEE

Capacity	14/2 to 10/4 BX 3/8" flexible metal conduit
Weight	1940 - 4 lbs (1.8 ka)

CAT. NO.	UPC NO.	DESCRIPTION
1940	34953	Flex Splitter® Flexible Metal Conduit Center
1941-1	00288	😯 Single Blade Replacement Blade for 1940
1941-5	33735	😯 5 Pack Replacement Blades for 1940



- Patented cutting wheel cuts clean and eliminates the need to debur the inside of the conduit.
- Simple to use-just tighten the screw, turn the tool around the conduit, and snap the conduit in two!
- · Heavy duty cast body for long life.
- · Large smooth spindle knob is easy to grip and doesn't hurt your hand.
- · Replaceable cutter wheel.

Cutting Capacity

CAT. NO.	UPC NO.	DESCRIPTION
8600	11915	Conduit Cutter
11917	11917	Cutter Wheel for 8600
SPECIFICATIONS		
Overall Ler	gth	FULLY OPEN - 8-1/4" (21.0 cm) • FULLY CLOSED - 7" (17.8 cm)
Weight		1.2 lb. (.55 kg)

Cuts 1/2" and 3/4" diameter EMT electrical conduit

SCREW AND NUT DRIVERS

5-Piece Screwdriver Set



- Heavy-duty construction for longer life.
- · Handle marked for easy identification of screwdriver size, type and length.
- · Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate tips prevents plate chipping and reduces slipping.
- High-grade, rust resistant, chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0153-01C	56303	5-Piece Screwdriver Set
0153-01C-CP	95930	5-Piece Screwdriver Set Counter Pack (Qty 5)

Contains	3/16" x 6" Cabinet, 1/4" x 4" Keystone, 1/4" x 6" Cabinet, 5/16" x 6"
	Keystone & #2 x 4" Phillips
Weight	1.38 lbs. (.63 ka)

0.55 lbs. (.25 kg)



7-Piece Screwdriver Set



- · Heavy-duty construction for longer life.
- Handle marked for easy identification of screwdriver size, type and length.
- Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate tips prevents plate chipping and reduces slipping.
- High-grade, rust resistant, chrome-plated finish.
- · Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0153-02C	54661	7-Piece Screwdriver Set
SPECIFICATION	DNS	
Contains		6" x 4" Cabinet, 3/16" x 6" Cabinet, 1/4" x 4" Keystone, 1/4" x 4"
	Cat	oinet, 5/16" x 6" Keystone, #1 x 3" Phillips & #2 x 4" Phillips
Weight	1.6	3 lbs. (.74- kg)

Heavy-Duty Keystone Tip Screwdriver



- Square shank allows use of wrench or pliers for added torque.
- Handle marked for easy identification of screwdriver size, type and length.

DESCRIPTION: HEAVY DUTY KEYSTONE TIP-

0.40 lbs. (.18 kg)

- Rugged keystone tip for additional strength.
- Precision-machined tips for accurate fastener contact.
- · Strong, durable black phosphate tips prevents plate chipping and reduces slipping.
- · Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

CAT. NO.

Weight

• Note: This is not an insulated tool.

	Overall Length	14-11/	32" (36.4 cm)	10-15/16" (27.8 cm)	13-7/16" (34.1 cm)
	SPECIFICATION	S 1.	/4" x 10"	5/16" x 6"	3/8" x 8"
	Weight	0.25	lbs. (.11 kg)	0.30 lbs. (.14 kg)	0.35 lbs. (.16 kg)
	Overall Length	8-11/3	32" (21.2 cm)	10-11/32" (26.3 cm)	12-11/32" (31.4 cm)
	SPECIFICATION	IS 1	I/4" x 4"	1/4" x 6"	1/4" x 8"
	0153-16C	56305	Square Sha	nk 3/8" x 8" Flat Blade	Screwdriver
1	0153-15C	56304	Square Sha	nk 5/16" x 6" Flat Blade	e Screwdriver
	0153-14C	54647		nk 1/4" x 10" Flat Blade	e Screwdriver
	0103-130-02	93929	Counter Pag	nk 1/4" x 8" Flat Blade ck (Qtv 10)	Screwuriver
	0153-13C 0153-13C-CP	54646 95929	•	nk 1/4" x 8" Flat Blade	
	0153-12C	54645	•	nk 1/4" x 6" Flat Blade	
	0153-11C	54644	•	nk 1/4" x 4" Flat Blade	

0.40 lbs. (.18 kg)



Heavy-Duty Cabinet Tip Screwdriver

GREENLEE



- Narrow cabinet tip for limited access applications.
- Handle marked for easy identification of screwdriver size, type and length.
- Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate tips prevents plate chipping and reduces slipping.
- · Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPT	ION: HEAVY D	UTY CABIN	IET TIP-	
0153-21C	54652	Round Sha	nk 3/16" x 4"	Flat Blade	Screwdriver	
0153-22C	54653		nk 3/16" x 6"	. iai Diaao	00.0	
0153-23C	54654	Round Sha	nk 3/16" x 8"	Flat Blade	Screwdriver	
0153-24C	54655	Round Sha	nk 3/16" x 10	" Flat Blade	e Screwdriver	
0153-25C	54649		nk 1/4" x 4" l	=		
0153-26C	54650		nk 1/4" x 6" l	=		
0153-27C	54651	Round Sha	nk 1/4" x 8" l	Flat Blade S	crewdriver	
SPECIFICATIO	NS 3/16	6" x 4"	3/16" x 6"	3/16" >	c 8" 3/1	6" x 10"
SPECIFICATIO			3/16" x 6" 3/4" (24.8 cm)		(8" 3/1 (8 cm) 13-3/4	
	7-3/4" ((19.7 cm) 9-			.8 cm) 13-3/4	
Overall Length	7-3/4" (0.15 lbs	(19.7 cm) 9-	3/4" (24.8 cm) 18 lbs. (.08 kg)	11-3/4" (29	.8 cm) 13-3/4	" (34.9 cm) os. (.10 kg)
Overall Length Weight	7-3/4" (0.15 lbs	(19.7 cm) 9- s. (.07 kg) 0.	3/4" (24.8 cm) 18 lbs. (.08 kg)	11-3/4" (29 0.20 lbs. (.0	.8 cm) 13-3/4 09 kg) 0.22 lt	" (34.9 cm) os. (.10 kg) x 8"
Overall Length Weight SPECIFICATIO	7-3/4" (0.15 lbs	(19.7 cm) 9- s. (.07 kg) 0.1 1/4" x 4"	3/4" (24.8 cm) 18 lbs. (.08 kg) 1/4 10-11/32	11-3/4" (29 0.20 lbs. (.0	.8 cm) 13-3/4 09 kg) 0.22 lt	" (34.9 cm) os. (.10 kg) x 8" 31.4 cm)

Stubby Screwdrivers



- · Precision-machined tips for exact fit.
- · Handle marked for easy identification of screwdriver size, type and length.
- Strong, durable black phosphate tips prevent plate chipping and reduce slipping.
- · Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION:
0153-28C 0153-32C	54648 54657	Round Shank 1/4" x 1-1/2" Flat Blade Screwdriver Heavy Duty Phillips Tip #2 - 1/4" x 1-1/2" Screwdriver
ODEOLEIOATI	ONO	4/40 4 4/00 4/40 4 4/00

SPECIFICATIONS	1/4" x 1-1/2"	#2 - 1/4" x 1-1/2"
Overall Length	3-1/8" (7.9 cm)	3" (7.6 cm)
Weight	0.10 lbs. (.05 kg)	0.10 lbs. (.05 kg)



Heavy-Duty Phillips Tip Screwdriver



- · Precision-machined tips for exact fit.
- Handle marked for easy identification of screwdriver size, type and length.
- Strong, durable black phosphate tips prevents plate chipping and reduces slipping.
- Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

Weight

• Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION	l	
0153-31C	54656	Heavy Duty Ph	nillips Tip #1 - 3/16" x 3	3" Screwdriver
0153-33C	54658	Heavy Duty Ph	nillips Tip #2 - 1/4" x 4"	' Screwdriver
0153-34C	54659	Heavy Duty Ph	nillips Tip #2 - 1/4" x 6"	' Screwdriver
0153-35C	54660	Heavy Duty Ph	nillips Tip #3 - 5/16" x 6	6" Screwdriver
SPECIFICATION	DNS #1	- 3/16" x 3"	#2 - 1/4" x 4"	#2 - 1/4" x 6"

Overall Length	11" (27.0 cm	1	
SPECIFICATIONS	#3 - 5/16" x	6"	
Weight	0.15 lbs. (.07 kg)	0.25 lbs. (.11 kg)	0.30 lbs. (.14 kg)
Overall Length	6-3/4" (17.2 cm)	8-5/16" (21.1 cm)	10-5/16" (26.2 cm)

0.35 lbs. (.16 kg)



6-In-1 Multi-Tool



- Versatile multi-bit screwdriver, 6 tools in one. (Bit sizes 3/16" & 1/4" Flat-tip, #1 & #2 Phillips and 5/16" & 1/4" Hex)
- · Precision machined, hardened steel bits.
- High-grade, rust resistant, chrome-plated finish.
- · Soft, cushioned grip for extra comfort and torque.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0153-42C	56308	6-In-1 Multi-tool
0153-42C-CP	95933	6-In-1 Multi-tool Counter Pack (Qty 5)
9953-13	56310	Replacement bits – 3/16" & 1/4" Flat-tip and #1 & #2 Phillips

Length	7-1/8" (20.6 cm)
Weight	.42 lbs. (.19 kg)
Bit Sizes	3/16" & 1/4" Flat-tip, #1 & #2 Phillips and 5/16" & 1/4" Hex

7-Piece Nut Driver Set

GREENLEE.



Heavy-Duty Nut Drivers



- Rugged hollow shaft for screw clearance.
- Heavy-duty construction for longer life.
- Handle color marked for easy identification of nut driver size.
- Precision heads for accurate fastener fit.
- High-grade, rust resistant, satin chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0253-11C	54664	Heavy-Duty Nut Driver 3/16" x 3"
0253-12C	54665	Heavy-Duty Nut Driver 1/4" x 3"
0253-13C	54666	Heavy-Duty Nut Driver 5/16" x 3"
0253-14C	54667	Heavy-Duty Nut Driver 11/32" x 3"
0253-15C	54668	Heavy-Duty Nut Driver 3/8" x 3"
0253-16C	54669	Heavy-Duty Nut Driver 7/16" x 3"
0253-17C	54670	Heavy-Duty Nut Driver 1/2" x 3-5/8"
CDECIEICATIO		9911 v 911 97011 v 911 771211 v 911 1 1/911 v 9 E/011

SPECIFICATIONS	3/16" x 3"	1/4" x 3"	5/16" x 3"
Overall Length	6-3/4" (29.8 cm)	6-3/4" (29.8 cm)	6-3/4" (29.8 cm)
Weight	0.20 lbs. (.09 kg)	0.20 lbs. (.09 kg)	0.20 lbs. (.09 kg)

SPECIFICATIONS	11/32" x 3"	3/8" x 3"	7/16" x 3"	1/2" x 3-5/8"
Overall Length	6-3/4" (29.8 cm)	6-3/4" (29.8 cm)	7-5/16" (18.6 cm)	7-5/16" (18.6 cm)
Weight	0.20 lbs. (.09 kg)	0.20 lbs. (.09 kg)	0.25 lbs. (.11 kg)	0.25 lbs. (.11 kg)

4-Piece Square-Recess Tip Driver Set



- · Precision tip for accurate fastener fit.
- Handle marked for easy identification of screwdriver size and type.
- Heavy-duty construction for longer life.
- High-grade, rust resistant, chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
 - Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION			
0353-01C	54695	4-Piece Square-Recess Tip Driver Set, Contains - #0, #1, #2 & #3			
SPECIFICATIONS					
Weight 1.0 lbs. (.45 kg)					

Square-Recess Tip Drivers



- · Precision tip for accurate fastener fit.
- Handle marked for easy identification of screwdriver size and type.
- Heavy-duty construction for longer life.
- High-grade, rust resistant, chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
- · Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.
- · Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRI	PTION		
0353-11C	54688	Square-	Recess Tip Drive	r - #0 x 4"	
0353-12C	54689	Square-	Recess Tip Drive	r - #1 x 4"	
0353-13C	54691	Square-	Recess Tip Drive	r - #2 x 4"	
0353-14C	54693	Square-	Recess Tip Drive	r - #3 x 4"	
SPECIFICATIO	NS #0	x 4"	#1 x 4"	#2 x 4"	#3 x 4"
Overall Lengt	h 7-3/4" (19.7 cm)	7-3/4" (19.7 cm)	8-1/4" (21.0 cm)	8-1/4" (21.0 cm)
Weight	0.20 lbs	(.09 kg)	0.20 lbs. (.09 kg)	0.30 lbs. (.14 kg)	0.30 lbs. (.14 kg)

Screw-Holding Screwdrivers



CAT. NO.	UPC NO.	DESCRIPTION:
0453-11C	56311	Screw-holding Screwdriver 3/32" x 3"
0453-12C	56312	Screw-holding Screwdriver 1/8" x 5"
0453-13C	56313	Screw-holding Screwdriver 5/32" x 5"
0453-14C	56314	Screw-holding Screwdriver 3/16" x 6"
0453-15C	56315	Screw-holding Screwdriver 1/4" x 7"
0453-16C	56316	Screw-holding Screwdriver #0 x 4"
0453-17C	56317	Screw-holding Screwdriver #1 x 5"
0453-18C	56318	Screw-holding Screwdriver #2 x 7"

- The industry's finest screw-holding device, available for either slotted or Phillips screws.
- Easily holds screw in place when installing in hard-to-reach locations.
- · Precision tip for accurate fastener fit.
- · Heavy-duty construction for longer life.
- Soft, cushioned grip for extra comfort and torque.
- · Handle marked for easy identification of screwdriver size and type.
- · Lifetime limited warranty.
- Note: This is not an insulated tool.

SPECIFICATIONS	3/32"	1/8"	5/32"	3/16"
Overall Length	6-5/8" (16.8 cm)	8-5/8" (21.9 cm)	8-5/8" (21.9 cm)	9-5/8" (24.5 cm)
Weight	.10 lbs. (.05 kg)	.16 lbs. (.07 kg)	.16 lbs. (.07 kg)	.20 lbs. (.09 kg)
SPECIFICATIONS	1/4"	#0	#1	#2
SPECIFICATIONS Overall Length	1/4" 11-1/8" (28.3 cm)	#0 7-5/8" (19.4 cm)	#1 8-5/8" (22.0 cm)	#2 11-1/8" (28.3 cm)

Conduit Reaming Screwdriver



- Deburs ID and OD of 1/2", 3/4" and 1" thin wall conduit.
- · Handle marked for easy identification.
- · Hardened blade for longer life.
- · Hooded, flat tip driver used to fasten EMT fittings.
- · Soft, cushioned grip for extra comfort and torque.
- Replaceable blade.
- · Lifetime limited warranty.
- · Note: This is not an insulated tool.

CA	AT. NO.	UPC NO.	DESCRIPTION
97	'53-11C	54696	Conduit Reaming Screwdriver
99	953-11	56319	Replacement blade, Conduit Reaming Screwdriver

SPECIFICATIONS

Capacity	1/2", 3/4" and 1"
Weight	.49 lbs. (.22 kg)
Overall Length	7-7/16" (18.9 cm)

Scratch Awl

GREENLEE



- Integrated steel endcap for durability and long life.
- Heavy-duty construction for piercing and scribing.
- · High-grade, rust resistant, chrome-plated finish.
- · Soft, cushioned grip for extra comfort.
- · Steel cap for easy identification.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION	
9753-12C	54697	Scratch Awl 3"	
SPECIFICATIONS			
Overall Length 7-7/8" ((20.0 cm)	
Weight .22 lbs. (.10 kg)		(.10 kg)	

ADJUSTABLE & RATCHETING WRENCHES

Composite Handle Adjustable Wrench



- Patented lightweight ergonomic design reduces user fatigue.
- Precision-machined to tight tolerances for professional feel and smooth operation.
- Compact reversible switch allows a 15° offset of the box end for clearance of obstacles.
- · Wide capacity jaw design provides extra versatility.
- Measuring scale on head for easy sizing.
- · Corrosion-resistant finish.
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION	DN	
0154-08C	56320	Adjustable V	Vrench Composite Handle	8"
0154-10C	56321	Adjustable V	Vrench Composite Handle	10"
0154-12C	56322	Adjustable V	Vrench Composite Handle	12"
SPECIFICATI	ons	8"	10"	12"

SPECIFICATIONS	8"	10"	12"
Overall Length	7-7/8" (20.0 cm)	9-13/16" (24.6 cm)	11-13/16" (30.0 cm)
Weight	0.66 lbs. (.24 kg)	1.03 lbs. (.48 kg)	1.36 lbs. (.62 kg)

Adjustable Wrench



- Precision-machined to tight tolerances for professional feel and smooth operation.
- · Wide capacity jaw design provides extra versatility.
- · Measuring scale on head for easy sizing.
- · Corrosion-resistant finish.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION	I	
0154-08	55483	Adjustable Wr	ench 8"	
0154-10	55484	Adjustable Wr	ench 10"	
0154-12	55485	Adjustable Wr	ench 12"	
SPECIFICATION	ONS	8"	10"	12"

SPECIFICATIONS	8"	10"	12"
Overall Length	7-7/8" (20.0 cm)	9-13/16" (24.6 cm)	11-13/16" (30.0 cm)
Weight	0.66 lbs. (.24 kg)	1.03 lbs. (.48 kg)	1.36 lbs. (.62 kg)

9-Piece Folding Hex-Key Set



- 9 piece set for convenience and versatility (including sizes 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4").
- One-piece, powder-coated handle/case for corrosion resistance.
- Heat-treated and tempered for extra strength and durability.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0254-11	56323	9-Piece Folding Hex-key Set: Sizes - 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32" & 1/4"

SPECIFICATIONS

Overall Length	4-3/8" (11.1 cm)
Weight	0.48 lbs. (.22 kg)

9-Piece Folding Ball-End Hex-Key Set



- 9 piece set for convenience and versatility (including sizes 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4").
- Ball-end design allows for angled use up to 30 degrees.
- One-piece, powder-coated handle/case for corrosion resistance.
- · Heat-treated and tempered for extra strength and durability.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0254-12	55482	9-Piece Folding Ball-end Hex-key Set: Sizes - 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32" & 1/4"

Overall Length	4-3/8" (11.1 cm)
Weight	0.48 lbs. (.22 kg)

G GREENLEE® A Textron Company

7-Piece Combination Ratcheting Wrench Set



- "Five-degree" ratcheting design for versatility and ease of use in tight spaces.
- Polished chrome finish for superior corrosion resistance.
- · Precision heads for accurate fastener fit.
- · Hardened for durability and longer life.
- · Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0354-01	55501	7-Piece Combination Ratcheting Wrench Set: Contains - Sizes 1/4", 5/16", 3/8", 7/16", 1/2", 9/16" & 5/8"
SPECIFICATI	ONS	
Weight	1.25 lb	s. (.57 kg)

Combination Ratcheting Wrenches



- "Five-degree" ratcheting design for versatility and ease of use in tight spaces.
- Polished chrome finish for superior corrosion resistance.
- Precision heads for accurate fastener fit.
- Hardened for durability and longer life.
- · Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRI	PTION		
0354-11	55494	Combina	ation Ratcheting V	Vrench 1/4"	
0354-12	55495	Combina	ation Ratcheting V	Vrench 5/16"	
0354-13	55496	Combina	ation Ratcheting V	Vrench 3/8"	
0354-14	55497	Combina	ation Ratcheting V	Vrench 7/16"	
0354-15	55498	Combina	ation Ratcheting V	Vrench 1/2"	
0354-16	55499	Combina	ation Ratcheting V	Vrench 9/16"	
0354-17	55500	Combina	ation Ratcheting V	Vrench 5/8"	
SPECIFICATIO	ONS 1	1/4"	5/16"	3/8"	7/16"
SPECIFICATION Overall Length			5/16" 5-5/16" (13.5 cm)	3/8" 6-1/8" (15.9 cm)	
	th 5-5/16"				6-1/2" (16.8 cm)
Overall Lengt	th 5-5/16" .09 lbs	(13.5 cm)	5-5/16" (13.5 cm) .08 lbs. (.08 kg)	6-1/8" (15.9 cm)	6-1/2" (16.8 cm)
Overall Lengt Weight	th 5-5/16" .09 lbs	(13.5 cm) . (.04 kg)	5-5/16" (13.5 cm) .08 lbs. (.08 kg)	6-1/8" (15.9 cm) .12 lbs. (.05 kg)	6-1/2" (16.8 cm) .16 lbs. (.07 kg)



INSULATED DRIVERS

6-Piece Insulated Screwdriver Set






- Rated to 1000 V AC/DC.
- Meets the IEC 60900 and ASTM F1505 standards.
- Heavy-duty construction for longer life.
- Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate plating prevents chipping and reduces slipping.
- Ergonomically designed handle for added comfort and torque.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0157-01I	56325	6-Piece Insulated Screwdriver Set Contains - 3/32" x 3", 5/32" x 4", 7/32" x 5", 1/4" x 6", #1 x 3-1/8" & #2 x 4"
SPECIFICATIO	ONS	
Weight	0.77 lb:	s. (.35 kg)

Insulated Screwdriver







- Rated to 1000 V AC/DC.
- · Meets the IEC 60900 and ASTM F1505 standards.
- Heavy-duty construction for longer life.
- Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate plating prevents chipping and reduces slipping.
- · Ergonomically designed handle for added comfort and torque.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION		
0157-11I	56326	Insulated Screv	wdriver 3/32" x 3"	
0157-12I	56327	Insulated Screv	wdriver 5/32" x 4"	
0157-13I	56328	Insulated Screv	wdriver 7/32" x 5"	
0157-14I	56329	Insulated Screv	wdriver 1/4" x 6"	
0157-17I	56332	Insulated Screv	wdriver #1 x 3-1/8"	
0157-18I	56333	Insulated Screv	wdriver #2 x 4"	
SPECIFICATION	ONS	3/32"	5/32"	7/32"

SPECIFICATIONS	3/32"	5/32"	1/32"
Overall Length	5-3/4" (14.6 cm)	7-7/8" (20 cm)	8-7/8" (22.6 cm)
Weight	.04 lbs. (.02 kg)	.05 lbs. (.13 kg)	.16 lbs. (.07 kg)
SPECIFICATIONS	1/4"	#1	#2
SPECIFICATIONS Overall Length	1/4" 10-1/4" (26 cm)	#1 7-1/8" (18.1 cm)	#2 8-1/4" (20.6 cm)

7-Piece Insulated Nut Driver Set



GREENLEE.




- Rated to 1000 V AC/DC.
- Meets the IEC 60900 and ASTM F1505 standards.
- Heavy-duty construction for longer life.
- Rugged deep well sockets for screw clearance.
- · Precision heads for accurate fastener fit.
- · Ergonomically designed handle for added comfort and torque.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0257-01 I	54679	7-Piece Insulated Nut Driver Set: Contains - Sizes 3/16", 1/4", 5/16", 11/32", 3/8", 7/16" & 1/2"
ODEOLEIOATI		

SPECIFICATIONS

Weight 1.40 lbs. (.64 kg)

Insulated Nut Driver



- Rated to 1000 V AC/DC.
- Meets the IEC 60900 and ASTM F1505 standards.
- Heavy-duty construction for longer life.
- Rugged deep well sockets for screw clearance.
- Precision heads for accurate fastener fit.
- Ergonomically designed handle for added comfort and torque.
- · Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
0257-11I	54672	Insulated Nut Driver 3/16" x 5"
0257-12I	54673	Insulated Nut Driver 1/4" x 5"
0257-13I	54674	Insulated Nut Driver 5/16" x 5"
0257-14I	54675	Insulated Nut Driver 11/32" x 5"
0257-15I	54676	Insulated Nut Driver 3/8" x 5"
0257-16I	54677	Insulated Nut Driver 7/16" x 5"
0257-17I	54678	Insulated Nut Driver 1/2" x 5"

SPECIFICATIONS	3/16"	1/4"	5/16"	11/32"
Overall Length	9-1/4" (23.5 cm)	9-1/4" (23.5 cm)	9-1/4" (23.5 cm)	9-1/4" (23.5 cm)
Weight	0.20 lbs. (.09 kg)			

SPECIFICATIONS	3/8"	7/16"	1/2"
Overall Length	9-1/4" (23.5 cm)	9-1/4" (23.5 cm)	9-1/4" (23.5 cm)
Weight	0.20 lbs. (.09 kg)	0.20 lbs. (.09 kg)	0.20 lbs. (.09 kg)



TAPE MEASURES, LEVELS, HAMMER & FLASHLIGHTS

Power-Return Tape Measures



- Blade automatically stays out when extended.
- · Bottom and top brake release.
- · Rigid double-sided tape for versatility and accuracy.
- Abrasion resistant blade for longer life.
- Multi-riveted double tang for added strength.
- Lifetime limited warrantv.

CAT. NO.	UPC NO.	DESCRIPTION
0155-25	55479	Power Return Tape Measure, double tang/sided, 25'
0155-16	55480	Power Return Tape Measure, double tang/sided, 16'

SPECIFICATIONS	25¹	16'
Tape Width	1" (2.5 cm)	3/4" (1.9 cm)
Weight	0.92 lbs. (.42 kg)	.58 lbs. (.26 kg)
Max. Standout	7'	6'

Mini Magnetic Bubble Level



- Professional grade level with bending offset aid.
- Mini torpedo design with handy "no-dog" attachment for bending.
- Three rare earth magnets provide superior holding strength.
- Four vial design 0°, 90°, 45°, and 30°.
- Machined from aluminum alloy and anodized to aircraft standards.
- Compact size fits easily in tool pouch.
- V-groove on top of level for easy view of vials.

CAT. NO.	UPC NO.	DESCRIPTION
L77	11617	Mini Magnetic Bubble Level

SPECIFICATIONS

Overall Length	5-1/2" (140 mm)
Width	3/4" (19 mm)
Height	1-1/2" (38 mm)
Weight	.22 lbs. (.10 kg)

Mini-Magnet Laser Level



- · Professional grade laser level.
- Mini torpedo design with handy "no dog" attachment for bending.
- Three rare earth magnets provide superior holding strength.
- Compact size with 80-plus yard range.
- · Laser is capable of working on all planes.
- Four vial design 0°, 90°, 45° and 30°.
- V-groove on top of level for easy view of vials.

1-3/4" (4.6 cm)

.46 lbs. (.21 kg)

Height Weight

Offsets and calculations permanently laser engraved onto level.

CAT. NO.	UPC NO.	DESCRIPTION
L97	03582	Laser Level
	-	
SPECIFICATIONS		
Overall Len	igth 5-5/8	3" (14.3 cm)
Width	3/4"	(1.9 cm)

Electrician's Torpedo Level

GREENLEE



- Professional grade level.
- · Four open vial ports for easy viewing from all sides.
- Perfect for pipe and conduit work.
- Four rare earth magnets allow for hands-free use on metal surfaces.
- Four vial design 0°, 30°, 45° and 90°.
- Machined from aluminum alloy and anodized to aircraft standards.
- V-groove on top of level for easy view of vials.

.34 lbs. (.16 kg)

· Offsets and calculations permanently laser engraved onto level.

CAT. NO.	UPC NO.	DESCRIPTION
L107	03583	Level, Torpedo
SPECIFICAT	IONS	
Overall Leng	gth 8-1/2	2" (21.6 cm)
Width	3/4"	(1.9 cm)
Height	1-1/4	4" (3.2 cm)

Electrician's Hammer



- Elongated neck and narrow striking face for use in boxes and other confined areas.
- Long straight claws designed for electrical fixture removal.
- Lightweight, durable fiberglass handle for shock resistance.
- Cushioned grip and flared handle end for user comfort and to reduce slipping.
- Exceeds ASME/ANSI specifications.
- · Lifetime limited warranty.

Weight

· Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0156-11	54698	18 oz. Electrician's Hammer
SPECIFICAT	IONS	

Overall Length 12-

Overall Length	12-1/2" (31.8 cm)
Weight	1.13 lbs. (.51 kg)

POCKET-LIGHT Flashlight



- · High intensity Xenon fired lamp.
- Dust and rust proof.
- · Luminous tip so flashlight can be located in the dark.
- Batteries included.
- · Lifetime limited warranty.
- Submersible to 500'.

CAT. NO.	UPC NO.	DESCRIPTION
46500	46500	Pocket-Light Flashlight
46533	46533	Lamp Module
46534	46534	0-Ring

MINI POCKET-LIGHT Flashlight



- High intensity Xenon fired lamp.
- Includes key ring and handy hat/ clothing clip.
- · Submersible to 500'.
- Batteries included.
- · Dust and rust proof.
- · Compact pocket and key chain light.

CAT. NO.	UPC NO.	DESCRIPTION
46503	46503	Mini Pocket-Light Flashlight
46533	46533	Lamp Module
46534	46534	0-Ring

TOOL BAGS, POUCHES, BELTS AND WORK GLOVES

20" Electrician's Bag



- Constructed of heavy-duty canvas for durability.
- Sixteen canvas, interior & exterior pockets for additional versatility.
- Full-grain leather bottom, sides and riveted buckle straps.
- Washer rivets for extra strength.
- Durable nylon handles with reinforced stitching fully support bag bottom for heavy load capacity.
- Reinforced bottom helps retain bag shape, while protecting and supporting tools.
- Large-opening steel-framed mouth with hinge for rugged use and easy access to contents.

CAT. NO.	UPC NO.	DESCRIPTION
0158-11	56334	20" Electrician's Canvas Bag
SPECIFICATIONS		
Dimensions	L - 20"	(50.8 cm), W- 12" (30.5 cm), H - 10" (25.4 cm)
Weight	4 25 lbs	s (1 93 km)

18" Heavy-Duty Multi-Pocket Bag



- Constructed of heavy-duty nylon for longer life.
- · Thirty-one multi-use reinforced pockets, inside and out help organize tools and accessories.
- · Large-opening steel-framed mouth with hinge and zipper for rugged use and easy access to contents.
- Padded handles and adjustable shoulder strap for comfort and versatility.
- Large interior to easily carry power tools, fish tapes and other large tools.
- Durable nylon handles with reinforced stitching fully support bag bottom for heavy load capacity.
- Elastic straps on outside of bag for levels, hammers and crowbars.

CAT. NO.	UPC NO.	DESCRIPTION
0158-12	56335	18" Heavy-Duty Multi-pocket Bag
SPECIFICATIONS		
Dimensions	Dimensions L - 18" (45.7 cm), W- 11" (27.9 cm), H - 10" (25.4 cm)	
Weight	3.55 lb	s. (1.61 kg)

11" Cordura® Open Tool Carrier



- Constructed of a double-layer of rugged, lightweight Cordura® fabric.*
- Versatile thirty-seven pocket and loop design keeps tools organized.
- · Large square opening with snap handle allows for easy access to spacious interior and pockets.
- Box-shaped design and sturdy reinforced bottom with rubber feet prevent
- · Heavy-duty box stitching with washer riveting at all stress points for extra strength and longer life.
- Padded handle, adjustable shoulder strap and additional built-in straps for extra versatility.
- · Heavy-duty tape measure holder accepts and holds any size tape securely.

CAT. NO.	UPC NO.	DESCRIPTION
0158-13	56336	11" Cordura Open Tool Carrier
SPECIFICATIONS		

Dimensions L - 11" (27.9 cm), W- 9" (22.9 cm), H - 10" (25.4 cm) Weight 4.55 lbs. (2.07 kg)

20-Pocket Tool Caddy

GREENLEE



- · Constructed of a double-layer of rugged, lightweight Cordura® fabric.*
- · Versatile twenty-pocket design easily accommodates a wide variety of professional hand tools.
- Large capacity pockets allow for easy access to contents.
- Padded handle and shoulder strap design for easy storage and the best way to carry a loaded tool pouch.
- · Heavy-duty tool snap and electrical tape strap.

- Steel hammer holder loop.
- Extra versatile design may be carried using shoulder strap or handle, or worn on a tool belt.
- · Heavy-Duty tape measure holder accepts and holds any size tape securely.

CAT. NO.	UPC NO.	DESCRIPTION
0158-15	56337	20-Pocket Tool Caddy
SPECIFICATION	ONS	
Dimensions	Dimensions L - 10" (25.4 cm), W- 7" (17.8 cm), H - 13" (33.0 cm)	
Weight	Weight 1.45 lbs. (.66 kg)	

*Cordura® is a registered trademark for durable fabric.

Heavy-Duty 8-Pocket Leather Pouch



- Large, divided main pocket area designed for easy storage and tool access.
- Four smaller compartments for additional tool organization.
- · Washer rivets for extra strength.
- Extra large metal tool clip.
- Tapered compartments for tool stability.
- Tape chain included.
- Fits belts up to 3" wide.
- Top grain leather won't fade or stain.
- · Heavy-Duty tape measure holder accepts and holds any size tape securely.

CAT. NO.	UPC NO.	DESCRIPTION
0258-11	56339	Heavy-Duty 8-Pocket Leather Pouch
SPECIFICATION	SPECIFICATIONS	
Dimensions	L - 7" (17.8 cm), W- 6" (15.2 cm), H - 10-1/2" (26.7 cm)
Weight	1.8 lbs. (.82 kg)	

Heavy-Duty 5-Pocket Leather Pouch



- · Large main pocket area designed for easy storage and tool access.
- · Four smaller compartments for additional tool organization.
- · Washer rivets for extra strength.
- · Extra large metal tool clip.
- · Tapered compartments for tool stability.
- · Tape chain included.
- Fits belts up to 3" wide.
- Top grain leather won't fade or stain.
- · Heavy-Duty tape measure holder accepts and holds any size tape securely.

CAT. NO.	UPC NO.	DESCRIPTION
0258-13	56340	Heavy-Duty 5-Pocket Leather Pouch

Dimensions	L - 6" (15.2 cm), W- 3-1/2" (8.9 cm), H - 11" (27.9 cm)
Weight	1.2 lbs. (.55 kg)

GREENLEE_®

Heavy-Duty 4-Pocket Leather Pouch



- Four compact pocket areas designed for easy storage and tool access.
- · Washer rivets for extra strength.
- Metal tool clip.
- Tapered compartments for tool stability.
- Tape chain included.
- Fits belts up to 3" wide.
- Top grain leather won't fade or stain.

CAT. NO.	UPC NO.	DESCRIPTION
0258-14	56341	Heavy-Duty 4-Pocket Leather Pouch
SPECIFICATION	ONS	

Dimensions	L - 5" (12.7 cm), W- 2-3/4" (7.1 cm), H - 9" (22.9 cm)
Weight	.43 lbs. (.82 ka)

Heavy-Duty Leather Tool Belt



- · 2" wide leather belt
- Steel roller double-pronged buckle
- Can be cut to fit 29" to 52" waist

CAT. NO.	UPC NO.	DESCRIPTION
9858-11	56347	Heavy Duty Leather Tool Belt

SPECIFICATIONS

Dimensions	L - 57" (121 cm), H - 2" (5.1 cm)
Weight	68 lbe (31 kg)

Padded Tool Belt



9858-12

- 5" wide padded tool belt.
- · Sturdy construction for support of heavy tool pouches.
- Foam core padding for extra comfort.
- Double layer of rugged, lightweight fabric will not rot, crack, harden or mildew.
- Steel roller double-pronged buckle.
- Made to fit 30" to 46" waist.

CAT. NO.	UPC NO.	DESCRIPTION
9858-12	56348	5" Padded Tool Belt

OI LOII IOAI IOIG	
Dimensions	L - 50" (12.7 cm), H - 5" (12.7 cm)
Weight	.93 lbs. (.42 kg)





12" Canvas Zipper Bag



- Constructed of heavy-duty canvas for durability.
- Strong zipper for secure closing.
- · Stores multiple small items or tools.

CAT. NO.	UPC NO.	DESCRIPTION
0158-14	56338	12" Canvas Zipper Bag

SPECIFICATIONS

Dimensions	L - 12" (30.5 cm), H - 7" (17.8 cm)
Weight	.17 lbs. (.08 kg)

2-Pocket Canvas Work Apron



- 2 large pockets to hold a variety of tools and miscellaneous small items.
- · Canvas waist ties.
- Double-stitched and reinforced at stress points for extra strength.
- Fits 20"-48" waist.

Weight

Weight

CAT. NO.	UPC NO.	DESCRIPTION		
0258-16	56342	2-Pocket Canvas String Apron		
SPECIFICATIONS				
Dimensions L = 10" (48.3 cm) H = 8-1/2" (21.6 cm)				

High Dexterity Gloves



- Tough, soft and comfortable to wear resists shrinking, stretching and hardening.
- Wing closing wrist strap for perfect adjustments, keeping debris out and easy-on/easy-off.
- Stretch fabric for flexibility and fit with padded knuckles.
- Textured palm pads for better grip, extra wear and added durability.
- Thumb design for better flexibility and Lycra side panels for improved dexterity.
- Terry cloth to remove sweat or debris from face.

.20 lbs. (.09 kg)

.18 lbs. (.08 kg)

CAT. NO.	UPC NO.	DESCRIPTION
0358-11XL 0358-11L	56343 56344	Gloves, Mechanics XL Gloves, Mechanics L
0358-11L-CP	95932	Gloves, Mechanics L Counter Pack (Qty 5)
SPECIFICATIONS		



TOOL KITS

Master Electrician's Tool Kit



0159-11



- All-inclusive tool kit designed with the master electrician in mind.
- Kit Includes: 18" Heavy-Duty Multi-pocket Bag, Heavy-Duty 8-Pocket Leather Pouch, 2" Leather Tool Belt, 9" Side-Cutting Pliers, 8" Diagonal Cutting Pliers, 8" Long Nose Pliers, 10" Pump Pliers, Pro Plus Wire Stripper 10-18 AWG, NM Cable Ripper, Stripping/Crimping Combination Tool, Cable Cutter, Utility Knife, 12" Hacksaw, Keystone Tip Square Shank 1/4" x 4" Flat Blade Screwdriver, Keystone Tip Square Shank 5/16" x 6" Flat Blade Screwdriver, Cabinet Tip Round Shank 3/16" x 6" Flat Blade Screwdriver, Cabinet Tip Round Shank 1/4" x 6" Flat Blade Screwdriver, Phillips Tip #1 3/16" x 3" Screwdriver, Phillips Tip #2 1/4" x 4" Screwdriver, Screwholding screwdriver 3/16" x 6", 3" Scratch Awl, 10" Adjustable Wrench, 9-Piece Folding Hex-Key Set, 25' Tape Measure, Torpedo Level, 18 oz. Electrician's Hammer, High dexterity gloves (L) and GT-11 Voltage tester.
- See individual product information for specifications.

CAT. NO.	UPC NO.	DESCRIPTION	
0159-11	56349	Master Electrician's Tool Kit, 28 pc	
SPECIFICATIONS			
Weight	10.7 lb	c (9.06 kg)	

Journeyman's Tool Kit



- Perfect kit for the journeyman electrician.
- Kit Includes: 20-Pocket Tool Caddy, GT-11 Voltage tester, Torpedo Level, 18 oz. Electrician's Hammer, 25' Tape Measure, Keystone Tip Square Shank 1/4" x 4" Flat Blade Screwdriver, Cabinet Tip Round Shank 3/16" x 6" Flat Blade Screwdriver, Phillips Tip #1 - 3/16" x 3" Screwdriver, Phillips Tip #2 - 1/4" x 4" Screwdriver, 9" Side-Cutting Pliers, 8" Diagonal Cutting Pliers, 8" Long Nose Pliers, 10" Pump Pliers, Pro Plus Wire Stripper 10-18 AWG, NM Cable Ripper, Stripping/Crimping Combination Tool and Cable Cutter.
- See individual product information for specifications.

CAT. NO.	UPC NO.	DESCRIPTION
0159-12	56350	Journeyman's Tool Kit, 17 pc
SPECIFICATI	ONS	
Weight	9.7 lbs	. (4.41 kg)

Electrician's Tool Kit

GREENLEE



- Perfect kit for the professional or apprentice electrician.
- Kit Includes: 2" Leather Tool Belt, 8-Pocket Leather Pouch, 25' Tape
 Measure, Phillips Tip #1 3/16" x 3" Screwdriver, Phillips Tip #2 1/4" x 4" Screwdriver, Cabinet Tip Round Shank 3/16" x 6" Flat Blade
 Screwdriver, Keystone Tip Square Shank 1/4" x 4" Flat Blade Screwdriver,
 Pro Plus Wire Stripper 10-18 AWG, 8" Long Nose Pliers, 10" Pump Pliers,
 8" Diagonal Cutting Pliers and 9" Side-Cutting Pliers.
- See individual product information for specifications.

CAT. NO.	UPC NO.	DESCRIPTION
0159-13	56351	Electrician's Tool Kit, 12 pc
SPECIFICATIONS		
Weight	7.75 lbs. (3.52 kg)	

Starter Electrician's Tool Kit



- Perfect kit for the beginner electrician.
- Four-pocket, heavy-duty, leather tool pouch holds an assortment of four professional grade hand tools.
- Kit Includes: Heavy Duty 4 Pocket Leather Pouch, Phillips Tip #2 1/4" x 4" Screwdriver, Cabinet Tip Round Shank 3/16" x 6" Flat Blade Screwdriver, Pro Plus Wire Stripper 10-18 AWG and 9" Side-Cutting pliers.
- See individual product information for specifications.

CAT. NO.	UPC NO.	DESCRIPTION
0159-14	56352	Starter Electrician's Tool Kit, 5 pc
SPECIFICATIONS		
Weight	2.25 lbs. (1.02 kg)	