
Carlon®





Carlon® ENT System

Electrical Non-Metallic Tubing (ENT) is an electrical raceway that has been used since 1980. when it was added to the National Electrical Code®. Electrical Non-Metallic Tubing is a pliable raceway that is used in concealed dry locations; concrete slabs; in walls and ceilings; raised floors for information technology equipment; and in buildings exceeding three floors from grade.

Features:


- UL® listed
- Lightweight
- Non-conductive
- Color coded
- · Hand bendable (pliable), no sharp edges
- Available in long-length coils and reels to reduce scrap

- Available in ½" (16) through 2" (53) sizes
- Available with a complete line of fittings and accessories that are compatible with Rigid Non-Metallic (PVC) Conduit and fittings
- Easy to work with no special tools required
- Speeds installation time


At T&B, we're committed to:


- Convenience of single-order, singleshipment to your site for thousands of stocking items
- Expert local point of contact for clear, consistent information regarding training, codes and standards
- Quality brands that have proven themselves over time
- Inventive design and manufacture of problem-solving products
- Offering a best-of-class warranty and returns policy


- Uniform carton labeling with additional bar-coding for
- Nationwide network of stocking electrical distributors
- Supplying you with the right products.
- convenient inventory management



convenient packaging, on-time delivery and competitive pricing











Customer Service

1-800-816-7809

Immediate, Knowledgeable Assistance

Every Thomas & Betts Customer Service Representative is right where the action is — surrounded by all the support and information they need to answer your questions and fill your orders faster than



ever. Your calls and faxes are automatically routed to Customer Service Specialists who personally serve your account and can answer questions about products, order status, price and availability, and other service-related inquiries.

Phone: 1-800-816-7809 **Fax:** 1-800-816-7810

Email: generalcustomerserviceteam@tnb.com

T&B Access®

tnbaccess.tnb.com

T&B Access® is a global sales tool for our distributor partners, offering:

- Quote Requests
- Stock Checks
- Pricing Inquiries
- Cross Reference
- Order Entry
- Order Resolution
- Shipping Status
- Document Look-Up

- Automatic Order Receiving
- Item History Search
- Multiple-Location User Search
- Context-Sensitive Help
- Shipping Confirmations



- Tracking Data
- Expediting
- · Returns Processing
- Quality Issues
- Customer Report Cards
- Web Catalog Look-Up

All of these tools and more are available online 24 hours a day -7 days a week, without having to make a single phone call. Multi-lingual options are available in English, French and Spanish. T&B Access® now serves over 10,000 satisfied customer users at over 3,500 locations every month.

Contents

T&B Services	2–3
Electrical Non-Metallic Tubing	4
Boxes and Accessories	5–14
Flexible Raceway Systems	15–23
Flexible Raceway System Accessories	24–28
Technical Information	29–30
Catalog Number Index	31–32







T&B Services

Technical Services

1-888-862-3289

Over 170 Years of Industry Experience

Meeting and exceeding our customers' expectations is a fundamental goal of Thomas & Betts. Call our Technical Services Department and talk LIVE to an expert who'll answer questions and concerns regarding all aspects of our products and services. Our experienced and knowledgeable staff is second to none in the industry!



Tool Services

1-800-284-T00L

Quality You Can Trust

Trust T&B's dedicated Tool Services Department to answer all questions regarding tool applications, repair, warranties, sales/lease/rental and technical information. Ask about our specialized services, including customer/sales training, demos and calibration/certification of tools.



Web Catalog

www.tnb.com/webcatalog

Thousands of Products at Your Fingertips

U.S. contractors and specifiers have made our web catalog their number one stop. Users can search for technical information by catalog number, UPC code, competitor number, keyword search, product category and/or brand. Having found the item(s) they are searching for, they can then use our *Where To Buy* function to locate a T&B local distributor and/or other support services.










T&B Services

Web CAD Library

www.tnb.com/CADLibrary

Over 4,000 2D and 3D CAD Models Available FREE!


The T&B CAD Library is an on-line source of 2D and 3D CAD models, available FREE to customers who register. Users can download these files to their desktops for import into their working drawings. Drawings are offered in 90 of the most popular native file formats. This is a valuable tool for CAD designers, OEMs and engineering firms, as it will allow them to quickly locate and download T&B drawings into their projects. Over 4,000 drawings of T&B® Fittings, PMA® Cable Protection, Kindorf®, Red•Dot® and Superstrut® products and Steel City® and Carlon® Floor Boxes are currently available, and we're continually adding more products to the library.



BIM Library

Now available to you through Autodesk® Seek (**seek.autodesk.com**), our BIM (Building Information Modeling) objects can easily be imported to your Revit® models. These BIM objects are fully standards compliant, Revit® Certified and completely configurable.

Autodesk and Revit are registered trademarks of Autodesk, Inc.







Fax: 901.252.1354

800.816.7809

<u>Carlon</u>

Electrical Non-Metallic Tubing

Flex-Plus® ENT

Flex-Plus® ENT is a non-metallic flexible raceway for use in walls, floors and non-plenum ceilings. It's lightweight, hand-bendable and free from sharp edges, which reduces installation time and saves money.

Options:

- Sizes ½" through 2"
- · Colors can designate different voltages. Examples:
 - Yellow color for communication circuits and signaling cable Red color for fire alarm circuits
- Blue color for power circuits
- Packaging: coils or reels







Standard Stock — Reels

	CAT. NO.	SIZE (IN.)	COLOR	NOM. I.D. (IN.)	NOM. O.D. (IN.)	PILL TAPE	MIN. BEND Radius (In.)	REEL SIZE (IN.) (F X W)	REEL TYPE (W=WOOD)	REEL LENGTH	REEL WT. (LBS.)	W I. PER 100 FT. (LBS.)
	12005AK-001	1/2	Blue	.56	.84	Empty	6	36 x 24	W	1500	40	10
	1205AKY-001	1/2	Yellow	.56	.84	Empty	6	36 x 24	W	1500	40	10
	1205AKR-001	1/2	Red	.56	.84	Empty	6	36 x 24	W	1500	40	10
*	▶ 12005AKC-001	1/2	Blue	.56	.84	Empty	6	36 x 24	W	1500	40	10
	12007AA-001	3/4	Blue	.76	1.05	Empty	6	36 x 24	W	1000	40	14
	1207AAY-001	3/4	Yellow	.76	1.05	Empty	6	36 x 24	W	1000	40	14
	1207AAR-001	3/4	Red	.76	1.05	Empty	6	36 x 24	W	1000	40	14
*	▶ 1207AAC-001	3/4	Blue	.76	1.05	Empty	6	36 x 24	W	1000	40	14
	12008-750	1	Blue	1.00	1.315	Empty	6	36 x 24	W	750	40	20
	12008Y-750	1	Yellow	1.00	1.315	Empty	6	36 x 24	W	750	40	20
	12008R-750	1	Red	1.00	1.315	Empty	6	36 x 24	W	750	40	20
*	▶ 12008C-750	1	Blue	1.00	1.315	Empty	6	36 x 24	W	750	40	20
	12009-750	11/4	Blue	1.402	1.66	Empty	7	48 x 32	W	750	90	19
	12010-750	1½	Blue	1.554	1.90	Empty	81/4	48 x 32	W	750	90	39
	12010Y-750	1½	Yellow	1.554	1.90	Empty	81/4	48 x 32	W	750	90	39
	12011-500	2	Blue	2.030	2.375	Empty	9½	48 x 32	W	500	90	32
	12011R-500	2	Red	2.030	2.375	Empty	9½	48 x 32	W	500	90	32
	12011V-500	2	Yellow	2 030	2 375	Emnty	Q1/ ₂	48 x 32	W	500	90	32

 $[\]begin{array}{ccc} \textbf{12011Y-500} & 2 & \text{Yellow} & 2 \\ *1\frac{1}{4}"-2" \text{ available in yellow \& red, made to order; consult factory.} \end{array}$

Standard Stock — Coils

	0175			NON	DII 1	MIN. BEND	COIL	WT. PER
CAT. NO.	SIZE (IN.)	COLOR	NOM. I.D. (IN.)	NOM. O.D. (IN.)	PILL Tape	RADIUS (IN.)	LENGTH (FT.)	100 FT. (LBS.)
12005-200	1/2	Blue	.56	.84	Empty	6	200	10
12005Y-200	1/2	Yellow	.56	.84	Empty	6	200	10
12005R-200	1/2	Red	.56	.84	Empty	6	200	10
* 12005C-370	1/2	Blue	.56	.84	Empty	6	200	10
12007-100	3/4	Blue	.76	1.05	Empty	6	100	14
12007Y-100	3/4	Yellow	.76	1.05	Empty	6	100	14
12007R-100	3/4	Red	.76	1.05	Empty	6	100	14
* 12007C-240	3/4	Blue	.76	1.05	Empty	6	100	14
12008-100	1	Blue	1.00	1.315	Empty	6	100	22
12008Y-100	1	Yellow	1.00	1.315	Empty	6	100	22
12008R-100	1	Red	1.00	1.315	Empty	6	100	22
* 12008C-160	1	Blue	1.00	1.315	Empty	6	100	22

10-ft. Lengths

Canada Only

CAT. NO.	SIZE (IN.)	COLOR	NOM. I.D. (IN.)	NOM. O.D. (IN.)	STD. CTN.	STD. WT. (LBS.)
12005-UPC	1/2	Blue	.56	.84	10 ft.	1.02
12007-UPC	3/4	Blue	.76	1.05	10 ft.	1.46
12008-010	1	Blue	1.00	1.315	10 ft.	2.93

Note: The solid blue color of ENT conduit is a registered trademark of Carlon®. ENT may show color deterioration in direct sunlight when stored outdoors over an extended period of time. It is suggested that all ENT products not be stored outside. Section 362.12(8) of the NEC® prohibits ENT to be used in areas exposed to direct sunlight.

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.



United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 **Technical Services**

Tel: 888.862.3289



Canada Only

Carlon[®]

Boxes and Accessories

Stub Downs

Vertical Stub Down

Carlon® Vertical Stub Downs are designed to provide a quick, easy connection to a wood deck or transition from slab-to-slab using Carlon's® "Quick Connect" snap-in design... simply snap the ENT in place. The integral snaps provide a secure mount — preventing the ENT from pulling out while enabling easy removal of the fitting once the deck is removed. All in a concrete-tight application. The underside of this fitting provides ample room to attach a Carlon® coupling to the ENT to continue the run. Carlon® Vertical Stub Downs are manufactured out of a highly engineered thermoplastic material to provide extra strength and durability and are available in sizes 1/2", 3/4" and 1".



CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A210D	1/2	50	3.8
A210E	3/4	50	3.7
A210F	1	50	4.8

Vertical Stub Down Transition Adapter

Carlon® Non-Metallic Exclusive...Carlon® Vertical Stub Down Transition Adapters, like our Vertical Stub Downs, provide a means to transition from ENT to another wire-management product where code requires other wire-management means. The integral snaps provide a secure mount - preventing the ENT from slipping or pulling out, while the deck-mount flange has a threaded port, enabling connection to other conduit system using a terminal adapter. Carlon® Vertical Stub Down Transition Adapters are manufactured out of polycarbonate material to provide extra strength and durability. They're concrete tight and available in sizes 1/2", 3/4" and 1".







CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A200D	½" Female ENT to NPSC (Female)	50	2.3
A200E	3/4" Female ENT to NPSC (Female)	50	2.8
A200F	1" Female ENT to NPSC (Female)	50	3.9

45° Stub Down

Carlon® 45° Stub Downs are designed to provide a smooth transition from cross-deck ENT runs to vertical applications. The integral snaps provide a secure mount — preventing the ENT from slipping or pulling out — but also enable the stub to easily be removed. The underside of this fitting provides ample room to attach a Carlon® coupling to the ENT to continue the run. Carlon® 45° Stub Downs are manufactured out of a highly engineered thermoplastic material to provide extra strength and durability. They're concrete tight and available in sizes ½", ¾" and 1".



CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A220D	1/2	25	1.8
A220E	3/4	25	2.0
A220F	1	25	2.6
A220G	111/4	25	2.8
A220H	1½	25	3.3
A220J	2	25	4.1

90° Stub Down Transition Adapter

Carlon® Non-Metallic Exclusive...Carlon® 90° Stub Downs are designed to provide a smooth transition from cross-deck ENT runs to vertical applications where code requires other wire-management means. The integral snaps provide a secure mount — preventing the ENT from slipping or pulling out, while the deck-mount flange has a threaded port, enabling connection to any conduit system using a terminal adapter. Carlon® 90° Stub Downs are manufactured out of polycarbonate material to provide extra strength and durability. They're concrete tight and available in sizes ½", ¾" and 1".







CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A230D	1/2" Female ENT to NPSC (Female)	25	2.0
A230E	3/4" Female ENT to NPSC (Female)	25	2.4
A230F	1" Female ENT to NPSC (Female)	25	3.3



Carlon®

Boxes and Accessories

Mud Box Assemblies

Carlon® Mud Box Assemblies are available in five unique styles…blank, ceiling ring, one-gang, two-gang and 4-inch square. All Mud Box Assemblies are manufactured out of polycarbonate material to provide extra strength and durability, are concrete tight and have twelve integral connectors…two 1", six ¾" and four ½". Using our new ENT Reducers, this product will meet ANY jobsite application.





Mud Box Base with Blank Cover

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A863BC ►	Mud Box with Blank Cover	24	12.3

Mud Box with Ceiling Ring

- Threaded brass inserts for fan (#10-32 screws) and fixture (#8-32 screws) mountings
- Listed for fixture support up to 50 lbs.
- Listed for ceiling fans up to 35 lbs.

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A863CF	Mud Box with Blank Cover	24	15.5
A863CFG ►	Mud Box with Ceiling Ring & Ground Lug	24	16.1



Mud Box with One-Gang Ring

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A863S	Mud Box with One-Gang Ring	24	16.8
A863SG ►	Mud Box with One-Gang	24	16.2
	Ring & Ground Lug		



CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A863D	Mud Box with Two-Gang Ring	24	15.8
A863DG ►	Mud Box with Two-Gang Ring	24	16.6
	& Ground Lug		

Mud Box with 4" Square Ring

4" Square Ring not for luminaire

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A863-4SQ ►	Mud Box with 4-Inch Square Ring	24	15.2

Mud Box Assemblies with Mounting Feet

Carlon® Mud Box Assemblies with Mounting Feet are specifically engineered and designed for use in Tunnel Form applications. The mounting feet are located on all four corners and enable the box to attach directly to the wall of the form using pop rivets. The pop rivets help keep the box in position during the pour and provide a safe, secure and rust-resistant mount.

CAT. NO.	IO. SIZE		STD. WT. (LBS.)
A863-4SQF	4-Square Ring	24	17.15
A863CFF	Ceiling Ring	24	16.61
A863CFGF	Ceiling Ring and Ground Lug	24	17.46
A863DF	Double-Gang	24	17.42
A863DGF	Double-Gang and Ground Lug	24	17.99
A863SF	Single-Gang	24	17.15
A863SGF	Single-Gang and Ground Lug	24	17.44











United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 **Technical Services** Tel: 888.862.3289






Carlon

Boxes and Accessories

Mounting Brackets

CARLON® EXCLUSIVE...The Carlon® ENT Mounting Bracket is specifically designed for use with Carlon® ENT Mud Box Assemblies in vertical concrete walls where one- or two-gang boxes are needed. The stainless steel spring-loaded mechanism provides a secure outlet box between concrete forms while the soft-steel strap enables the outlet box to be secured to rebar. The bracket combination ensures a straight box opening and a concrete-tight fit. Mud Box not included.



ENT Bridge

CARLON® EXCLUSIVE...The Carlon® ENT Bridge is designed to support long ENT runs in concrete pour applications. This makes pulling wire/cable a snap. Installation is easy...simply mount the ENT bridge, using nails or screws, to the wood deck mounting and snap the ENT into place. The bridge is designed to hold the conduit in place while minimizing dips in the conduit over long runs. The Carlon® ENT Bridge is manufactured out of a highly engineered thermoplastic material to provide extra strength and durability and can accommodate ENT sizes ½", ¾" and 1". (The Carlon® ENT bridge can be used with rigid non-metallic conduit too.)

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A293DEF	ENT Bridge	50	9.0





Fax: 901.252.1354

800.816.7809



Boxes and Accessories

Transition Adapters

Male ENT to Schedule 40 and 80 PVC Conduit

CARLON® EXCLUSIVE...Carlon® Male ENT to Schedule 40 & 80 PVC Conduit Transition Adapters are designed to connect Schedule 40 conduit to Carlon® Flex-Plus® Blue™ ENT boxes and fittings. Simply solvent cement the PVC adapter to the Schedule 40 conduit and snap the adapter into Carlon's® "Quick Connect" snap-in connector on the box or fitting. Carlon® Male ENT to Schedule 40 & 80 Adapters are concrete tight and available in sizes ½", ¾" and 1".

Carlon
Exclusive

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A263D	½" ENT to ½" Sch. 40 or Sch. 80	100	2.4
A263E	3/4" ENT to 3/4" Sch. 40 or Sch. 80	100	3.2
A263F	1" ENT to 1" Sch. 40 or Sch. 80	100	4.5





ENT to EMT

Carlon® ENT to EMT Transition Adapters are designed to easily transition from Carlon® Flex-Plus® Blue™ ENT to EMT using Carlon's® "Quick Connect" snap-in design. The EMT is held securely in place using the small screw (provided). This helps prevent the EMT from slipping/shifting out of the adapter. All ENT to EMT adapters are manufactured out of polycarbonate material to provide extra strength and durability. They're concrete tight and available in sizes 1/2", 3/4" and 1".

047.110		STD.	STD. WT.
CAT. NO.	SIZE	CTN.	(LBS.)
A245D	½" ENT to ½" EMT	100	3.4
A245E	3/4" ENT to 3/4" EMT	100	4.1
A245F	1" ENT to 1" EMT	100	5.4





Reducers

CARLON® EXCLUSIVE...Carlon® ENT Reducers are designed to provide an easy transition from 1" Carlon® ENT to 3/4" ENT or from 3/4" Carlon® ENT to 1/2" ENT. They're concrete tight and manufactured out of polycarbonate material to provide extra strength and durability. Carlon® ENT Reducers provide flexibility while on the jobsite by minimizing the need to carry size-specific boxes and fittings. Carlon® ENT Reducers provide the versatility to convert Carlon® fittings and boxes to many different sizes and configurations.

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A273DE	3/4"-1/2"	100	3.2
A273EF	1"-3/4"	100	2.4











Boxes and Accessories

Outlet and Switch Boxes — Eccentric Knockouts

CARLON® EXCLUSIVE...Carlon® ENT Outlet and Switch Boxes with Eccentric Knockouts are designed to enable selective ENT openings — ½", ¾" and 1" — based on application needs. They provide the largest capacity available on the market today — 22 cu. in. Single-Gang, and 38 cu. in. Double-Gang — and can be mounted to wood or steel studs. Carlon® ENT Outlet and Switch Boxes with Eccentric Knockouts are manufactured out of a highly engineered thermoplastic material to provide extra strength and durability and are available in single-gang and double-gang styles.





Note: The double-gang version is also a 4-in. square box.

Single-Gang — 22 Cu. In.

CAT. NO.	SIZE	CAPACITY Cu. In.	STD. CTN.	STD. WT. (LBS.)
A122	Single-Gang	22	25	6.8

UL Classified for 2-hour-or-less fire-resistant fire wall assemblies





Combination Two-Gang/Four-Inch Square Box — 38 Cu. In.

CAT. NO.	SIZE	CAPACITY Cu. In.	STD. CTN.	STD. WT. (LBS.)
A238	Two-Gang	38	25	8.9

UL Classified for 2-hour-or-less fire-resistant fire wall assemblies

Outlet Box Divider

Carlon® ENT Outlet Box Divider is specifically designed for applications where a combined high- and low-voltage closed-back box is needed, such as for placement in a fire-rated wall. Just slip the divider into place to get the split box you need. The Carlon® ENT Outlet Box Divider is UL® Recognized for use with the Carlon® A238 Box only.



		STD.	STD. WT.
CAT. NO.	SIZE	CTN.	(LBS.)
4000DU/		F0	4.07
A238DIV	_	50	1.87



Carlon®

Boxes and Accessories

Quick-Connect Adapters and Couplings

- Carlon® one-piece ENT Quick-Connect Couplings, Threaded Adapters and Snap-In Terminator Adapters are suitable for damp locations
- Quick-Connect Couplings and Threaded Adapters are concrete-tight when used with Carlon[®] ENT
- All sizes of rigid non-metallic conduit fittings are compatible with ENT when using ENT cement
- Rigid non-metallic conduit fittings are recommended for use with Carlon[®] 1¹/₄"-2" Flex-Plus[®] Blue[™] ENT
- Use of ENT Blue[™] Quick-Set Cement is required; see page 14 for details

 When One-Piece Quick-Connect Snap-In Terminator Adapters are installed in a concrete application, Carlon[®] flat sealing washers must be used on the box connection ends





86720 LR92248

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A240D	1/2	150	2.90
A240E	3/4	100	3.00
A240F	1	50	2.30

Threaded Adapters

Couplings

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A243D	1/2	150	2.55
A243E	3/4	100	2.30
A243F	1	50	2.00

Snap-In Adapters

onap minaap	1010		
CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A253D	1/2	150	2.70
A253E	3/4	100	2.90
A253F	1	50	2.30








Rigid Non-Metallic Conduit Adapters and Couplings

Male Terminal Adapters

For adapting nonmetallic conduits to boxes, threaded fittings, metallic systems. Male threads on one end, socket end on other.






CAT.		STD.	TYP	ICAL		MAX.	T	/PICA	L	STD. WT.
NO.	SIZE	CTN.	Α	В	MIN. D	OD	C	S	L	(LBS.)
E943D	1/2	150	.852	.836	.597	11//8	5/8	⁹ ⁄ ₁₆	15/16	2.8
E943E	3/4	125	1.064	1.046	.800	111/32	3/4	⁹ ⁄ ₁₆	13/8	3.5
E943F	1	50	1.330	1.310	1.018	11/8	1	11/16	125/32	3
E943G	11/4	50	1.677	1.655	1.332	21/32	1	3/4	1 15/ ₁₆	4
E943H	11/2	25	1.918	1.894	1.566	25/32	13/16	3/4	21/16	2.5
E943J	2	50	2.393	2.369	2.000	$2^{21}/_{32}$	¹³ / ₁₆	3/4	21/8	7

Standard Couplings

All socket fittings should be attached using ENT Blue™ Quick-Set Cement (**page 14**). Using Carlon® fittings with Carlon® non-metallic conduit ensures system integrity.



Socket type for joining non-metallic conduit.



(P)

LR31146

CAT.		STD.	STD TYPICAL		- MAX		TYPICAL		- STD. WT.
NO.	SIZE	CTN.	A	В	MIN. D	OD	С	L	(LBS.)
E940D	1/2	150	.852	.836	.728	17/64	11/16	1½	2.8
E940E	3/4	100	1.064	1.046	.840	15/16	3/4	1%	3.5
E940F	1	50	1.330	1.310	1.210	11/8	¹⁵ / ₁₆	2	3
E940G	11/4	30	1.677	1.655	1.535	$1^{63}/_{64}$	1	21/8	4
E940H	11/2	25	1.918	1.894	1.755	215/64	11//8	23/8	2.5
E940J	2	30	2.393	2.369	2.190	247/64	13/16	21/2	7

*All measurements in inches, unless otherwise noted.



*All measurements in inches, unless otherwise noted.

United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 Technical Services
Tel: 888.862.3289





Boxes and Accessories

21/211 and 411 Mud Boxes and Covers

UL® Classified for 2-hour-or-less fire-resistant floor/ceiling assemblies

Base Rings

Listed for use with ceiling fans up to 35 lbs. and for fixture support up to 50 lbs.







CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A861	Without Ground Lug	10	2.5
C861G	With Ground Lug	10	2.0



Covers

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A862D	2½ Deep (½" KOs)	10	2.5
A862E	2½ Deep (¾" KOs)	10	2.1
A864D	4 Deep (½" KOs)	10	2.9
A864E	4 Deep (¾" KOs)	10	2.9
A864F	4 Deep (1" KOs)	10	3.0



Quick-Connect Outlet and Switch Boxes

- Suitable for masonry walls
- Meets NEMA OS-2
- UL Classified for 2-hour-or-less fire-resistant wall assemblies



Single-Gang — 16 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A58381D	3 x 21/4 x 3 (1/2" KOs)	25	4.6
A58381E	3 x 21/4 x 3 (3/4" KOs)	25	4.6



4" Square — 20 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A52151D	4 x 4 x 1½ (½" KOs)	100	22.6
A52151E	4 x 4 x 1½ (¾" KOs)	100	22.6
A521DE	4 x 4 x 1½ (½" & ¾" KOs)	100	22.6



4" Square — 30.3 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A52171D	4 x 4 x 2¾ (½" KOs)	25	7.6
A52171E	4 x 4 x 23/8 (3/4" KOs)	25	7.6
A5217DE	4 x 4 x 23/8 (1/2" & 3/4" KOs)	25	7.6





United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354





Carlon®

Boxes and Accessories

ENT Box with Adapters

UL® Classified for 2-hour-or-less fire-resistant wall assemblies



4" Square — 2	<u>"</u>		
CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A5329DE	4 x 4 x 1¾ (½" & ¾" KOs)	50	14.8
	,		

UL Listed E42728



Box Back Wall Support

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
A540DS	For use with 1/2" Knockout	100	2.1



ENT Box Extenders

UL® Classified for 2-hour-or-less fire-resistant wall assemblies



Single-Gang

- J J				
CAT. NO.	RISE (IN.)	CU. IN.	STD. CTN.	STD. WT. (LBS.)
A410	1/2	3.5	100	7.7
A411	5/8	4.2	50	4.6
A412	3/4	5.0	50	5.1
A413	1	6.6	40	5
A414	11/4	8.1	30	4.4



i wo-uang				
CAT. NO.	RISE (IN.)	CU. IN.	STD. CTN.	STD. WT. (LBS.)
A400	Blank	_	100	7.7
A420	1/2	6.1	75	5.0
A421	5/8	7.4	50	4.2
A422	3/4	8.8	50	4.8









United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354







Boxes and Accessories


Round Covers for Octagon Ceiling Boxes

Round Plaster Rings

- Listed for fixture support up to 50 lbs.
- UL® Classified for 2-hour-or-less fire-resistant assemblies



E42	728
. WT. (LBS.)	





Round Blank Covers

CAT. NO.	RISE	CU. IN.	STD. CTN.	STD. WT. (LBS.)
E460R-CAR	Blank	_	35	2.2
A470D	Blank with 1/2" KO	_	100	4.7



Quick Connect 4" Octagon Ceiling Boxes

- Carlon® ceiling boxes and round plaster rings are produced from a special high heat-resistant engineered plastic material developed specifically for fixture support
- Listed for fixture support up to 50 lbs.
- UL® Classified for 2-hour-or-less fire resistant floor/ceiling assemblies



Ceiling Box — 20.5 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A615D	(4) 21/8 Deep (1/2" KOs)	50	6.4
A615E	(4) 21/8 Deep (3/4" KOs)	50	6.4
A615DE	(4) 21/8 Deep (1/2" & 3/4" KOs)	50	6.4



Ceiling Box with J Mount — 20.5 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A615DJ	(4) 21/8 Deep (1/2" KOs)	50	18.7



Ceiling Box with L Bracket — 20.5 Cu. In.

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A615DL	(4) 21/8 Deep (1/2" KOs)	50	6.4



Ceiling Box with Adjustable Hanger Bar — 20.5 Cu. In.

coming box	man rajactable manger zan		
CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
A615DH	(4) 21/8 Deep (1/2" KOs)	25	13.6

Adjust from 141/4" to 231/4"







Carlon

Boxes and Accessories

PVC Conduit Cutters

Small Cutter

For fast, smooth field cuts of $\frac{1}{2}$ " through 1" Flex-Plus® Blue™ ENT.



CAT. NO.	SIZE (IN.)	STD. CTN.
CC120B	8	10

Medium Cutter

Handheld cutter makes fast, square, smooth field cuts on conduit from $\frac{1}{2}$ " through $\frac{1}{4}$ ". Produces burr-free cut with no shavings. Fits into pocket or pouch.



CAT. NO.	SIZE (IN.)	STD. CTN.
CC125	9	12

Large Cutter

For clean cuts of conduit 1/2" through 2".



CAT. NO.	SIZE (IN.)	STD. CTN.
CC122	17½	1

Concrete Sleeves

Non-metallic concrete sleeve forms are the easy way to form holes in concrete. They install in seconds with nails, screws or staples and are easily removed. Concrete will not adhere to them. Concrete sleeves are adjustable to any slab thickness.



CAT. NO.	MIN. O.D. A (IN.)	B (IN.)	STD. CTN.	STD. WT. (LBS.)
E92CSH	1½	1¾	20	3
E92CSJ	2	213/32	25	6
E92CSL	3	313/32	25	8
E92CSN	4	413/32	18	8
E92CSP	5	$5^{13}/_{32}$	15	8
E92CSR	6	613/32	12	8

Tape

Prelubricated, woven polyester tape made from low-friction, high abrasion-resistant yarns, providing a low coefficient of friction. Tape is printed with sequential footage markings for accurate measurements.



CAT. NO.	SIZE (IN.)	TENSILE Strength (LBS.)	REEL Lengths (Ft.)
TL14505	1/2	1250	5000
TL14510	1/2	1250	10000
TL38203	5/8	1800	3000
TL38265	5/8	1800	6500
TL38210	5/8	1800	10000

Other tapes are available. Consult your sales service location for additional information.

Carlon® Low VOC Cement

(MSDS sheets available at www.carlon.com)

All Weather — ENT Blue

RECOMMENDED PIPE APPLICATION AND SIZES		UP TIME Ation rate)	RECOMMENDED Installation Temp.		SHEAR 73° F	VISCOSITY AT 75° F AS MANUFACTURED
Required for use with Flex-Plus® ENT	-5°−10° F	6–8 Minutes	-5° to 100° F	2 Hrs.	350 PSI	400-700 CPS
(Electrical Non-Metallic Tubing),	10°-30° F	4-5 Minutes		16 Hrs.	800 PSI	
Riser-Gard®, P&C Flex™ and Carlon®	30°-50° F	3-4 Minutes		72 Hrs.	1500 PSI	
PVC fittings.	50°-70° F	1-2 Minutes				
Up through 6" diameter.	70°-90° F	1/2-11/2 Minutes				



ENT cement required for use with ENT and Rigid Non-Metallic Conduit Fittings.

CAT. NO.	SIZE	APPLICATOR	DESCRIPTION	STD. CTN.	STD. WT. (LBS.)
VC9992	Quart	Dauber	All-Weather "Quick-Set" Blue	12	29.0
Monto ACTM D OFCA					





Carlon®

Flexible Raceway Systems

Carlon® Plenum-Gard® Raceway

Plenum-Gard® is a UL® Listed non-metallic corrugated flexible conduit for use in plenum, riser and general purpose applications. Plenum-Gard® is manufactured from PVDF resin, which is extremely durable and resistant to abrasion and mechanical damage before/after cable installation.

Plenum-Gard® is listed to UL® 2024 in accordance with the National Electrical Code® for plenum, riser, general purpose and other cabling/optical fiber/telecommunication applications as defined in Articles 725, 770, 800 and 820.

Important: Installed cables must be plenum rated and the UL® Listing must be printed on the product. Abandoned cables MUST be removed (reference NEC®).

Technical Info

UL STANDARD 2024	VALUE
Maximum Flame Propagation	5 ft.
Max. Peak Optical Smoke Density	0.5
Max. Average Optical Smoke Density	0.15

• Storage: -4° to 158° F

Handling: -4° to 104° F

No UV protection (not suitable for outdoor use)

Do not store outside



Applications: Plenum, Riser and General Purpose

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.



Standard Stock — Reels

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	REEL SIZE (F X W) (IN.)	REEL TYPE	REEL Length (Ft.)	REEL WT.(LBS.)	REEL WT. PER 100 FT. (LBS.)
CD4X1C-1500	1/2	Orange	200 lb.	34 x 23	Wood	1,500	30	7
CE4X1-1000		Orange	Empty	34 x 23	Wood	1,000	30	8
CE4X1-1000S	3/4	Orange	Empty/Split	34 x 23	Wood	1,000	30	8
CE4X1C-1000		Orange	900 lb.	34 x 23	Wood	1,000	30	8
CF4X1C-500		Orange	900 lb.	34 x 23	Wood	500	30	10
CF4X1C-1000		Orange	900 lb.	48 x 28	Wood	1,000	79	10
CF4X1C-1500	1	Orange	900 lb.	48 x 28	Wood	1,500	79	10
CF4X1C-5200		Orange	900 lb.	66 x 41	Wood	5,200	250	10
CF4X1C-6500		Orange	900 lb.	72 x 41	Wood	6,500	310	10
CF4X1C-8000		Orange	900 lb.	82 x 41	Wood	8,000	365	10
CG4X1C-500		Orange	900 lb.	48 x 28	Wood	500	79	14
CG4X1-500S		Orange	Empty/Split	48 x 28	Wood	500	79	10
CG4X1C-900		Orange	900 lb.	48 x 45	Wood	900	96	14
CG4X1C-1600	11/4	Orange	900 lb.	48 x 45	Wood	1,600	96	14
CG4X1C-3200		Orange	900 lb.	66 x 41	Wood	3,200	250	14
CG4X1C-6500		Orange	900 lb.	96 x 41	Wood	6,500	700	14
CG4X1-900S		Orange	Empty/Split	48 x 28	Wood	900	79	14
CH4X1C-350		Orange	900 lb.	48 x 28	Wood	350	79	16
CH4X1C-1200	1½	Orange	900 lb.	48 x 45	Wood	1,200	96	16
CH4X1C-4000		Orange	900 lb.	82 x 41	Wood	4,000	365	16
CJ4X1-200S		Orange	Empty/Split	48 x 28	Wood	200	79	21
CJ4X1C-225		Orange	900 lb.	48 x 28	Wood	225	79	21
CJ4X1C-700	2	Orange	900 lb.	48 x 45	Wood	700	96	21
CJ4X1C-1400		Orange	900 lb.	82 x 41	Wood	1,400	365	21
CJ4X1C-2000		Orange	900 lb.	82 x 41	Wood	2,000	365	21
CJ4X1C-2800		Orange	900 lb.	82 x 41	Wood	2,800	365	21
CL4X1C-150	3	Orange	900 lb.	48 x 45	Wood	150	96	41



Carlon® Plenum-Gard® Raceway (continued)

- For use in plenum areas per NEC® Articles 725, 770, 800 and 820
- Sizes ½" through 3"
- Pre-installed pull tape available in sizes ½" through 3"
- Outside diameters meet IPS dimensions
- UL® Listed raceway meeting UL 2024
- Footage sequentially marked
- Single-peak design

Standard Stock — Coils

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	COIL LENGTH (FT.)	PRODUCT WT. PER 100 FT.(LBS.)
CD4X1C-500	1/2	Orange	900 lb.	500	7
CE4X1-350*	3/4	Orange	Empty	350	8
CE4X1-350S		Orange	Empty/Split	350	8
CF4X1C-100*		Orange	900 lb.	100	10
CF4X1-100S*		Orange	Empty/Split	100	10
CF4X1C-250*	1	Orange	900 lb.	250	10
CF4X1-250		Orange	Empty	250	10
CF4X1-250S*		Orange	Empty/Split	250	10
CG4X1C-200*	11/4	Orange	900 lb.	200	14
CG4X1-200S		Orange	Empty/Split	200	14
CH4X1C-150*	1½	Orange	900 lb.	150	16
CH4X1-150S		Orange	Empty/Split	150	16
CJ4X1C-100*	2	Orange	900 lb.	100	21
CJ4X1-100S		Orange	Empty/Split	100	21

^{*} Overnight Shippable

Specifications

SIZE (IN.)	I.D. MIN. REF. (IN.)	MIN. O.D. (IN.)	MAX. O.D. (IN.)	MIN. BEND RADIUS (IN.)
1/2	.60	.815	.835	2
3/4	.74	1.025	1.045	2
1	1.00	1.292	1.312	3
11/4	1.35	1.630	1.650	3
1½	1.50	1.868	1.888	4
2	2.00	2.329	2.439	4
3	3.00	3.422	3 452	4

Custom Orders — How to Build a Part Number:

POSITION 1 Product	POSITION 2 Size (In.)	POSITION 3 Type	POSITION 4 Wall	POSITION 5 COLOR	POSITION 6 Pull line	POSITION 7 Length
C = Plenum-Gard	D = ½	4 = Corrugated	X = Standard	1 = Orange	C = 900 LB. Tape	Example
	$E = \frac{3}{4}$			2 = Black		-1000 = Feet
	F = 1			3 = Gray		-1000S = 1000 Feet Split
	G = 11/4			4 = White		
	H = 1½			5 = Blue		
	J = 2			7 = Yellow		
	L = 3			8 = Red		

- Custom orders are not returnable
- Custom lengths are available in minimum order quantities of 1,000 ft.
- Custom color runs are available in minimum order quantities of 10,000 ft.

- Options: Color: Black, Blue, Gray, Red, White and Yellow
 - · Two-, three- or four-way parallel
 - Split duct
 - Custom print line



United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

Technical Services

Tel: 888.862.3289



Carlon[®]

Flexible Raceway Systems

Carlon® Riser-Gard® Raceway

Riser-Gard® is a non-metallic flexible raceway for use in riser and general purpose applications. Riser-Gard® is UL® Listed and is available with tape pre-installed. Riser-Gard is listed to UL® 2024 Standard for riser applications or optical fiber/communications raceways.

Riser-Gard® is listed to UL® 2024 in accordance with the National Electrical Code® per Articles 725, 770, 800 and 820 for riser, general purpose and other cabling/optical fiber/telecommunication applications. Riser-Gard® is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum.

Important: Installed cables must be of suitable rating for the application.

Technical Info

UL LISTED TO 2024	TEST METHOD	MAXIMUM VALUE
Maximum Flame Propagation	UL 2024	6.0 ft.
Maximum Air Temperature at 12 ft.	UL 2024	372° F

- Storage: -4° to 158° F
- Handling: -4° to 104° F
- No UV protection (not suitable for outdoor use)
- Do not store outside



Applications: Riser and General Purpose

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.



Standard Stock — Reels

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	REEL SIZE (F X W) (IN.)	REEL TYPE	REEL Length (Ft.)	REEL WT.(LBS.)	REEL WT. PER 100 FT. (LBS.)
DE4X1-1000	3/4	Orange	Empty	34 x 23	W	1,000	30	12
DF4X1C-500R		Orange	900 lb.	43 x 23	W	500	56	15
DF4X1C-1000		Orange	900 lb.	48 x 28	W	1,000	79	15
DF4X1C-1500		Orange	900 lb.	48 x 28	W	1,500	79	15
DF4X1C-2700	1	Orange	900 lb.	48 x 45	W	2,700	96	15
DF4X1C-5200		Orange	900 lb.	66 x 41	W	5,200	250	15
DF4X1C-6500		Orange	900 lb.	72 x 41	W	6,500	310	15
DF4X1C-7000		Orange	900 lb.	72 x 45	S	7,000	148	15
DF4X1C-9400		Orange	900 lb.	84 x 45	S	9,400	199	15
DG4X1C-900		Orange	900 lb.	48 x 28	W	900	79	17
DG4X1C-500R		Orange	900 lb.	48 x 23	W	500	56	17
DG4X1C-1500		Orange	900 lb.	48 x 45	W	1,500	96	17
DG4X1C-1600	1¼	Orange	900 lb.	48 x 45	W	1,600	96	17
DG4X1C-3200		Orange	900 lb.	66 x 41	W	3,200	250	17
DG4X1C-4500		Orange	900 lb.	72 x 45	S	4,500	148	17
DG4X1C-5600		Orange	900 lb.	82 x 41	W	5,600	365	17
DG4X1C-6500		Orange	900 lb.	96 x 41	S	6,500	700	17
DH4X1C-1200		Orange	900 lb.	48 x 45	W	1,200	96	22
DH4X1C-4000	1½	Orange	900 lb.	82 x 45	S	400	193	22
DH4X1C-4500		Orange	900 lb.	84 x 45	S	4,500	199	22
DJ4X1C-700		Orange	900 lb.	48 x 45	W	700	96	27
DJ4X1C-2000	2	Orange	900 lb.	82 x 41	W	200	265	27
DJ4X1C-2800		Orange	900 lb.	84 x 45	S	2,800	199	27
DL4X1C-750	3	Orange	900 lb.	72 x 41	W	750	310	27
W = Wood	S = Steel							



Carlon® Riser-Gard® Raceway (continued)

Features:

- For use in riser and general purpose areas per NEC® Articles 725, 770, 800 and 820
- Riser-Gard® is also suitable for direct burial, not approved for exposed applications

Note: UL has not evaluated Riser-Gard® for this application.

- UL® Listed raceway meeting UL 2024
- Available in sizes ¾" through 3"
- Pull tape can be factory pre-installed in 1" through 3"
- · Outside diameters meet IPS dimensions
- Footage sequentially marked

Standard Stock — Coils

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	COIL LENGTH (FT.)	PRODUCT WT. PER 100 FT.(LBS.)
DE4X1-350*	3/4	Orange	Empty	350	12
DF4X1C-125		Orange	900 lb.	125	15
DF4X1C-250*		Orange	900 lb.	250	15
DF4X1-250	1	Orange	Empty	250	15
DF4X1C-500		Orange	900 lb.	500	15
DF4X1-250S*		Orange	Empty/Split	250	15
DG4X1-200		Orange	Empty	200	17
DG4X1-200S*	11/4	Orange	Empty/Split	200	17
DG4X1C-200*		Orange	900 lb.	200	17
DG4X1C-500		Orange	900 lb.	500	17
DH4X1-150S	1½	Orange	Empty/Split	150	22
DH4X1C-150*		Orange	900 lb.	150	22
DJ4X1-100S	2	Orange	Empty/Split	100	27
DJ4X1C-100*		Orange	900 lb.	100	27
DL4X1C-250	3	Orange	900 lb.	250	27

^{*} Overnight Shippable

Specifications

оросписатопо				
SIZE (IN.)	I.D. MIN. REF. (IN.)	MIN. O.D. (IN.)	MAX. O.D. (IN.)	MIN. BEND RADIUS (IN.)
3/4	.74	1.025	1.075	5
1	.98	1.290	1.340	6
1¼	1.31	1.640	1.690	8
1½	1.54	1.880	1.930	10
2	2.00	2.350	2.400	12
3	3.00	3.422	3.452	18

Custom Orders — How to Build a Part Number:

POSITION 1 Product	POSITION 2 Size (In.)	POSITION 3 Type	POSITION 4 Wall	POSITION 5 Color	POSITION 6 Pull line	POSITION 7 Length
D = Riser-Gard	E = ¾	4 = Corrugated	X = Standard	1 = Orange	C = 900 lb. Tape	Example
	F = 1			2 = Black		-1000 = Feet
	G = 11/4			3 = Gray		-1000S = 1000 Feet Split
	H = 1½			4 = White		
	J = 2			5 = Blue		
	L = 3			7 = Yellow		
				8 = RED		

- Custom orders are not returnable
- Custom lengths are available in minimum order quantities of 1,000 ft.
- Custom color runs are available in minimum order quantities of 10,000 ft.
- Options: Color: Black, Blue, Gray, Red, White and Yellow
 - · Two-, three- or four-way parallel
 - Split duct
 - Custom print line



United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

Technical Services Tel: 888.862.3289





Carlon® Hal-Free Riser-Gard® Raceway

Hal-Free Riser-Gard® is a halogen-free non-metallic flexible raceway for use in riser and general purpose applications. In the event of a fire, this product will not release halogen elements into the air, which makes it ideal for applications in tunnels, laboratories and high-tech environments. Hal-Free Riser-Gard® is listed to UL® 2024 in accordance with NEC® Articles 725, 770, 800 and 820. Custom lengths and split ducts are available upon request. Hal-Free Riser-Gard® is available in white only.

Features:

- Free from halogen elements
- Compliant with NEC® Articles 725, 770, 800 and 820
- Available in sizes 1" through 2"
- · Available in white only
- Sequentially marked footage



Applications: Riser and General Purpose

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

Technical Info

UL LISTED TO 2024	TEST METHOD	MAXIMUM VALUE
Maximum Flame Propagation	UL 2024	3' 6" ft.
Maximum Air Temperature	III 2024	387° F

- Storage and Handling: -4° to 150° F
- No UV protection (not suitable for outdoor use)
- Do not store outside



Standard Stock — Reels

						REEL SIZE		REEL		
CAT. NO.	SIZE (IN.)	COLOR	NOM. I.D (IN.)	NOM. O.D. (IN.)	PULL TAPE	(F X W) (IN.)	REEL TYPE	LENGTH (FT.)	REEL WT. (LBS.)	PRODUCT WT. PER 100 FT. (LBS.)
HF4X4C-5000	1	White	1.049	1.365	900 lb.	72" x 41"	W	5,000	310	7.5
HG4X4C-4000	11/4	White	1.250	1.550	900 lb.	72" x 41"	W	4,000	310	7.5
HH4X4C-2000	1½	White	1.500	1.850	900 lb.	66" x 41"	W	2,000	250	12
HJ4X4C-2000	2	White	2.000	2.425	900 lb.	82" x 41"	W	2,000	365	21

Custom Orders — How to Build a Part Number:

POSITION 1 Product	POSITION 2 SIZE (IN.)	POSITION 3 Type	POSITION 4 Wall	POSITION 5 COLOR	POSITION 6 Pull line	POSITION 7 Length
H = Hal-Free	F = 1	4 = Corrugated	X = Standard	4 = White	C = 900 lb. Tape	Example
	G = 11/4					-1000 = Feet
	H = 1½					-1000S = 1000 Feet Split
	.1 – 2					

- · Custom orders are not returnable
- · Custom lengths are available in minimum order quantities of 1,000 ft.



800.816.7809 Fax: 901.252.1354



Carlon

Flexible Raceway Systems

Carlon® Plenum Duct

Technical Info:

- Maximum flame propagation distance is less than 5.0 ft.
- · Peak optical density of smoke is less than 0.50
- · Average optical density of smoke is less than 0.15
- UL® Listed to UL 2024 Standard
- FT-6 Rated



Standard Stock — Reels

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	REEL SIZE (IN.)	REEL LENGTH (FT.)	REEL WT. (LBS.)	PRODUCT WT. PER 100 FT. (LBS.)
PLM100T-500		White	900 lb.	34 x 23	500	30	10
PLM100T-1800	1	White	900 lb.	48 x 28	1,800	79	10
PLM100T-5000		White	900 lb.	72 x 41	5,000	310	10
PLM100T-8000		White	900 lb.	82 x 41	8,000	365	10
PLM125T-500		White	900 lb.	34 x 23	500	30	14
PLM125T-1000	11/4	White	900 lb.	48 x 30	1,000	83	14
PLM125T-5000		White	900 lb.	72 x 41	5,000	310	14
PLM125T-6000		White	900 lb.	82 x 41	6,000	365	14
PLM150T-2000	1½	White	900 lb.	66 x 41	2,000	250	14
PLM150T-4000		White	900 lb.	82 x 41	4,000	365	14
PLM200T-2000	2	White	900 lb.	82 x 41	2,000	365	21

Standard Stock — Coils/Box

CAT. NO.	SIZE (IN.)	COLOR	PULL TAPE	BOX SIZE (IN.)	COIL LENGTH (FT.)	PRODUCT WT. PER 100 FT. (LBS.)
PLM100T-250B2	1	White	900 lb.	34 x 14 x 34	250	10
PLM125T-250B4	1¼	White	900 lb.	39 x 15 x 39	250	14

Specifications

SIZE	I.D. MIN. REF.	MIN. O.D.	MAX. O.D.	MIN. BEND RADIUS
1/2	.60	.815	.835	2
3/4	.74	1.025	1.045	2
1	1.00	1.292	1.312	3
1¼	1.35	1.630	1.650	3
1½	1.50	1.868	1.888	4
2	2.00	2.329	2.439	4

Custom Orders — How to Build a Part Number:

Guotom Gruoro	non to buil	a a r art mannson	
POSITION 1 Product	POSITION 2 Size (In.)	POSITION 3 Pull line	POSITION 4 Length
PLM = PLENUM	100 = 1 125 = 1¼ 150 = 1½ 200 = 2	T = 900 lb. Tape	Example -1000 = Feet

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.



Fax: 901.252.1354





Carlon® Riser Duct

Technical Info:

- · Maximum flame propagation: 6.0 ft. max. value
- · Do not store outside
- No UV protection
- UL® Listed to UL 2024
- FT-4 Rated



Applications: Riser and General Purpose Applications per NEC® Articles 725, 770, 800 and 820. Suitable for vertical runs in a shaft or between floors.

Standard Stock — Reels

CAT. NO.	SIZE (IN.)	COLOR	PULL Tape	REEL SIZE (IN.)	REEL LENGTH (FT.)	REEL WT. (LBS.)	PRODUCT WT. PER 100 FT. (LBS.)
RIS100T-5000	1	Orange	900 lb.	66 x 41	5,000	250	15
RIS125T-4000	11/4	Orange	900 lb.	72 x 41	4,000	310	17
RIS150T-2000	1½	Orange	900 lb.	66 x 41	2,000	250	22
RIS200T-2000	2	Orange	900 lb.	66 x 41	2,000	250	27

Specifications

SIZE (IN.)	I.D. MIN. REF. (IN.)	MIN. O.D. (IN.)	MAX. O.D. (IN.)	MIN. BEND RADIUS (IN.)
3/4	.74	1.025	1.075	6
1	.98	1.290	1.340	6
11/4	1.31	1.640	1.690	7
11/2	1.54	1.880	1.930	81/4
2	2.00	2.350	2.400	91/2

Custom Orders — How to Build a Part Number:

POSITION 1 Product	POSITION 2 SIZE (IN.)	POSITION 3 Pull line	POSITION 4 LENGTH
RIS = Riser	$100 = 1$ $125 = 1\frac{1}{4}$ $150 = 1\frac{1}{2}$ $200 = 2$	T = 900 lb. Tape	Example -1000 = Feet

Carlon® Hal-Free Riser Duct

Technical Info:

- · Maximum flame propagation: 6.0 ft. max. value
- Do not store outside
- No UV protection
- UL® Listed to UL 2024 Standard
- FT-4 Rated

Applications: Riser and General Purpose Applications per NEC® Articles 725, 770, 800 and 820.

Standard Stock — Reels

			PULL	REEL	REEL LENGTH	REEL WT.	PRODUCT WT. PER 100 FT.
CAT. NO.	SIZE (IN.)	COLOR	TAPE	SIZE (IN.)	(FT.)	(LBS.)	(LBS.)
RHF100T-5000	1	White	900 lb.	66 x 41	5,000	250	15
RHF125T-4000	11/4	White	900 lb.	72 x 41	4,000	310	17
RHF150T-2000	1½	White	900 lb.	66 x 41	2,000	250	22
RHF200T-2000	2	White	900 lb.	82 x 41	2.000	365	27

Specifications

SIZE (IN.)	I.D. MIN. Ref. (IN.)	MIN. O.D. (IN.)	MAX. O.D. (IN.)	MIN. BEND RADIUS (IN.)
3/4	.74	1.025	1.075	6
1	.98	1.290	1.340	6
11/4	1.31	1.640	1.690	7
11/2	1.54	1.880	1.930	81/4
2	2.00	2.350	2.400	91/2

Custom Orders — How to Build a Part Number:

POSITION 1 Product	POSITION 2 SIZE (IN.)	POSITION 3 Pull line	POSITION 4 LENGTH
RHF = Hal-Free Riser	$100 = 1$ $125 = 1\frac{1}{4}$ $150 = 1\frac{1}{2}$ $200 = 2$	T = 900 lb. Tape	Example -1000 = Feet





Small. Slick. Speedy. Ideal for Telecom Installs! Carlon® Micro-Gard® Plenum and Micro-Gard® Riser Duct

Carlon® Micro-Gard® Plenum and Micro-Gard® Riser is specifically designed to provide fiber pathways in plenum and riser applications in Multi-Dwelling Units (MDUs) and other premise structures


The 8/6 and 12/10 mm size conduits can be installed individually or used to optimize space in existing duct structures. And the small size significantly reduces the structural damage caused during pass-throughs.


Micro-Gard® Plenum and Riser is UL® Listed for plenum and riser applications. It's easy to handle, easy to install and easy to conceal, making it the ideal MDU cable management system.

Features:

- UL® and cUL Listed to UL 2024 for plenum and riser applications
- Compliant with NEC® Articles 725, 770, 800 and 820
- Two sizes: 8/6mm and 12/10mm. The smaller sizes accommodate the size constraints of multi-dwelling units and make installations faster and easier
- Smooth interior wall eliminates snag points and provides low coefficient of friction, regardless of whether jetting or pull-tape is used
- Superior burn-through resistance for longer cable pulls
- Pre-lubricated, factory installed pull-tape makes installing cable faster and easier (option available for empty duct)
- Sequentially marked footage to easily identify lengths and reduce waste
- Reel sizes from 1,000 to 5,000 feet for easy handling on the jobsite
- · Future-proofing raceway system for fast, easy wire/cable upgrades, changes and moves
- Used in cable bundles

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.











Carlon® Micro-Gard® Plenum and Micro-Gard® Riser

CAT. NO.	SIZE	ТҮРЕ	COLOR	FACTORY INSTALLED	PRE-LUBRICATED Radius (In.)*	MIN. BEND Feet/Reel	REEL Size (In.)
MGP08MT-1000	8/6 mm	Plenum	White	50 lb. Cord	2	1,000	24
MGP08MT-2500	8/6 mm	Plenum	White	50 lb. Cord	2	2,500	24
MGP08MT-5000	8/6 mm	Plenum	White	50 lb. Cord	2	5,000	36
MGP12MT-1000	12/10 mm	Plenum	White	50 lb. Cord	4	1,000	24
MGP12MT-2500	12/10 mm	Plenum	White	50 lb. Cord	4	2,500	24
MGP12MT-5000	12/10 mm	Plenum	White	50 lb. Cord	4	5,000	36
MGR08JT-1000	8/6 mm	Riser	Orange	50 lb. Cord	2	1,000	24
MGR08JT-2500	8/6 mm	Riser	Orange	50 lb. Cord	2	2,500	24
MGR08JT-5000	8/6 mm	Riser	Orange	50 lb. Cord	2	5,000	36
MGR12JT-1000	12/10 mm	Riser	Orange	50 lb. Cord	4	1,000	24
MGR12JT-2500	12/10 mm	Riser	Orange	50 lb. Cord	4	2,500	24
MGR12JT-5000	12/10 mm	Riser	Orange	50 lb. Cord	4	5,000	36

^{*}NOTE: Do not exceed the minimum bend radius during installation of the product.

Micro-Gard® Plenum Dimensions — Smooth O.D./Ribbed I.D.

	OUTSIDE DIAMETER		WAL	L	INSIDE DIA. (MIN.)			– STD. WT.
CAT. NO.	INCH	ММ	INCH	ММ	INCH	ММ	# RIBS	(LB./100 FT.)
MGP12RMT	.472 +/004	12 +/1	.047 +0/004	1 +0/1	.354	8.9	26	4.92
MGP08RMT	.315 +/004	8 +/1	.040 +0/004	1 +0/1	.212	5.4	16	2.68

Micro-Gard® Riser Dimensions — Smooth O.D./Ribbed I.D.

	OUTSIDE DIAMETER		WAL	L	INSIDE DIA. (MIN.)			– STD. WT.
CAT. NO.	INCH	ММ	INCH	ММ	INCH	MM	# RIBS	(LB./100 FT.)
MGR12RJT	.472 +/004	12 +/1	.047 +0/004	1 +0/1	.354	8.9	26	2.86
MGR08RJT	.315 +/004	8 +/1	.040 +0/004	1 +0/1	.212	5.4	16	1.55

How to Interpret a Catalog Number

POSITION 1 Product	POSITION 2 Type	POSITION 3 Size	POSITION 4 COLOR	POSITION 5 Pull line	POSITION 6 LENGTH
MG = Micro-Gard	P = Plenum	08 = 8/6mm	J = Orange	T = 50 lb. Cord	Example
	R = Riser	12 = 12/10mm	M = White		-1000 = Feet



800.816.7809

Fax: 901.252.1354

Carlon[®]

Flexible Raceway System Accessories

For use with Riser-Gard® and General Purpose Non-Metallic Adapters and Couplings



Couplings

CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	STD. WT. (LBS.)
SCA240E	3/4	Orange	25	.783
SCA240F	1	Orange	20	.972



Threaded Adapters

CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	STD. WT. (LBS.)
SCA243E	3/4	Orange	100	2.30
SCA243F	1	Orange	50	2.00



Snap-In Adapters

				STD. WT.
CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	(LBS.)
SCA253E	3/4	Orange	100	2.90
SCA253F	1	Orange	50	2.30



For use with Plenum-Gard® Non-Metallic Adapters and Couplings



Couplings

CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	STD. WT. (LBS.)
A340F	1	Orange	50	2.50



Threaded Adapters

CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	STD. WT. (LBS.)
A343F	1	Orange	50	1.55



Snap-In Adapters

CAT. NO.	SIZE (IN.)	COLOR	STD. CTN.	STD. WT. (LBS.)
A353F	1	Orange	50	3.00









Flexible Raceway System Accessories


For use with Riser-Gard® and General Purpose



Non-Metallic Male Terminal Adapters

For adapting non-metallic conduits to boxes, threaded fittings, metallic systems. Male threads on one end, socket end on other.






				DIMENSIONS (IN.)						STD.	
CAT.	SIZE	STD.		TYP	TYPICAL		MIN. MAX		TYPICAL		
NO.	(IN.)		COLOR	Α	В	D	0.D.	C	T	L	(LBS.)
E943E	3/4	125	Gray	1.064	1.046	.800	111/32	3/4	% 16	1%	3.5
E943F	1	50	Gray	1.330	1.310	1.018	15/8	1	11/16	$1^{25}/_{32}$	3
E943G	11/4	50	Gray	1.677	1.655	1.332	21/32	1	3/4	1 15/16	4
E943H	11/2	25	Gray	1.918	1.894	1.566	25/32	1 ½16	3/4	21/16	2.5
E943J	2	50	Gray	2.393	2.369	2.000	$2^{21}/_{32}$	1 ½16	3/4	21/8	7
SCE943G	11/4	50	Orange	1.677	1.655	1.332	21/32	1	3/4	1 15/16	4
SCE943H	11/2	25	Orange	1.918	1.894	1.566	25/32	1 ½16	3/4	21/16	2.5
SCE943J	2	50	Orange	2.393	2.369	2.000	$2^{21}/_{32}$	1 ½16	3/4	21/8	7

Non-Metallic Standard Couplings

All socket fittings should be attached Using Carlon® solvent cement. Using Carlon® fittings with Carlon® non-metallic conduit ensures system integrity.



				DIMENSIONS (IN.)						
CAT.	SIZE	STD.		TYP	TYPICAL		MAX.	TYPI	CAL	STD. WT.
NO.	(IN.)	CTN.	COLOR	Α	В	MIN. D	0.D.	C	L	(LBS.)
E940E	3/4	100	Gray	1.064	1.046	.840	1 5/16	3/4	1%	4.4
E940F	1	50	Gray	1.330	1.310	1.210	1%	15/16	2	3.5
E940G	11/4	30	Gray	1.677	1.655	1.535	1 ⁶³ / ₆₄	1	21/8	3.5
E940H	11/2	25	Gray	1.918	1.894	1.755	$2^{15}/_{64}$	11//8	23/8	3.9
E940J	2	30	Gray	2.393	2.369	2.190	$2^{47}/_{64}$	13/16	21/2	5.25
SCE940G	11/4	30	Orange	1.677	1.655	1.535	$1^{63}/_{64}$	1	21/8	3.5
SCE940H	11/2	25	Orange	1.918	1.894	1.755	$2^{15}/_{64}$	11//8	23/8	3.9
SCE940J	2	30	Orange	2.393	2.369	2.190	$2^{47}/_{64}$	13/16	2½	5.25

For use with Plenum-Gard®

Metallic Terminal Adapter

259



CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
255	3/4	10	12
256	1	100	25
257	11/4	100	28
258	11/2	100	35

Flat Sealing Washer

Where a waterproof termination is required into any enclosure (metallic or non-metallic), install the neoprene washer over the threads of a terminal adapter before inserting into the enclosure. Use a standard locknut or threaded bushing to secure the assembly.



CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)
► E943EW	3/4	125	.45
► E943FW	1	100	.46
► E943GW	11/4	50	.44
► E943HW	1½	50	.45
► E943JW	2	25	.42

800.816.7809 Fax: 901.252.1354





Carlon[®]

Flexible Raceway System Accessories

Low-Voltage Boxes and Brackets



Dual-Voltage Box/Bracket*

E11461

CAT. NO.	COVER	VOLUME	STD. CTN.	STD. WT. (LBS.)
SC200DV	1-Gang	20.5 cu. in	16	6.4

*U.S. Patent D463,376.



Low-Voltage Add-On Bracket*

E137781

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)
SC100SC	1-Gang	24	2.3

*U.S. Patent D459,312.

U.S. Patent 6,710,245.

U.S. Patent 6,872,884.



Low-Voltage Adjustable Brackets*

LISTED E137781

CAT. NO.	SIZE	STD. CTN.	STD. WT. (LBS.)	
SC100ADJC	1-Gang	24	7.5	
SC200ADJC	2-Gang	20	6.9	

*U.S. Patent 5,289,934.



Low-Voltage Brackets*

E137781


CAT. NO.	SIZE	RESI-RINGS	STD. CTN.	STD. WT. (LBS.)
SC100A	1-Gang	3/4, 1, 11/4	24	5.3
SC200A	2-Gang	3/4, 1, 11/4	24	7.7
SC300A	3-Gang	_	5	1.6

*U.S. Patent D457,140. U.S. Patent D462,664.

U.S. Patent 6,812,405.

For other Carlon® Flexible Raceway System Accessories, refer to the following pages:

- Mud Box Assemblies p. 6
- Mud Boxes and Covers p. 11
- Quick-Connect Outlet and Switch Boxes p. 11
- ENT Box and Extenders p. 12
- Octagon Ceiling Boxes and Covers p. 13
- Cutting Tools p. 14



SC100SC

SC200DV

SC100ADJC



Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354





Flexible Raceway System Accessories

Carlon® Low-VOC Cements

*Meets ASTM D2564

Medium — Clear

modium oloui					
RECOMMENDED PIPE APPLICATION AND SIZES		UP TIME ATION RATE)	RECOMMENDED INSTALLATION TEMP.	LAP SHEAR @ 73° F	VISCOSITY AT 75° AS MANUFACTURED
Recommended for all grades	10°–30° F	Not recommended	40° to 100° F	2 Hrs. 350 psi	500-900 cps
and types of Carlon® wireway	30°-50° F	5-6 minutes		16 Hrs. 800 psi	
and fittings, except Flex-Plus®	50°-70° F	3-4 minutes		72 Hrs. 1,500 psi	
Blue™ ENT (Electrical Non- Metallic Tubing.)	70°–90° F	1–2 minutes			

Up through 6" diameter.

CAT. NO.	SIZE	APPLICATOR	DESCRIPTION	STD. CTN.	STD. WT. (LBS.)
VC9963	Pint	Dauber	PVC Medium Clear	24	29.0
VC9962	Quart	Dauber	PVC Medium Clear	12	27.5
VC9961P	Gallon	_	PVC Medium Clear	6	53.5
Meets ASTM D-2564.					



Regular — Clear

RECOMMENDED PIPE APPLICATION AND SIZES		UP TIME ATION RATE)	RECOMMENDED INSTALLATION TEMP.	LAP SHEAR @ 73° F	VISCOSITY AT 75° AS MANUFACTURED
Recommended for all grades	10°–30° F	Not recommended	40° to 100° F	2 Hrs. 350 psi	500–900 cps
and types of Carlon® wireway	30°-50° F	5-6 minutes		16 Hrs. 800 psi	
and fittings, except Flex-Plus®	50°-70° F	3-4 minutes		72 Hrs. 1,500 psi	
Blue [™] ENT (Electrical Non- Metallic Tubing.)	70°–90° F	1–2 minutes			

Up through 6" diameter.

(LBS.)	CTN.	DESCRIPTION	APPLICATOR	SIZE	CAT. NO.
6.5	10	PVC Regular Clear	Dauber	½ Pint	VC9964
	10	PVC Regular Clear	Dauber	½ Pint	VC9964





Fax: 901.252.1354



Flexible Raceway System Accessories

Carlon® Low-VOC Cements (continued)

All Weather — Clear

RECOMMENDED PIPE APPLICATION AND SIZES		P TIME TION RATE)	RECOMMENDED INSTALLATION TEMP.	LAP SHEA	.R @ 73° F	VISCOSITY AT 75° AS MANUFACTURED
Recommended for all grades and	-5°-10° F	6–8 Minutes	-5° to 100° F	2 Hrs.	350 PSI	400-700 CPS
types of Carlon® wireway and fittings,	10°–30° F	4-5 Minutes		16 Hrs.	800 PSI	
except Flex-Plus® Blue™ ENT	30°-50° F	3-4 Minutes		72 Hrs.	1,500 PSI	
(Electrical Non-Metallic Tubing.)	50°-70° F	1-2 Minutes				
Up through 6" diameter.	70°–90° F	1/2-11/2 Minutes				

CAT. NO.	SIZE	APPLICATOR	DESCRIPTION	STD. CTN.	STD. WT. (LBS.)
VC9984	½ Pint	Dauber	All Weather "Quick-Set" Cement	10	7.0
VC9983	Pint	Dauber	All Weather "Quick-Set" Cement	24	30.0
VC9982	Quart	Dauber	All Weather "Quick-Set" Cement	12	29.0
VC9981P	Gallon	_	All Weather "Quick-Set" Cement	6	54.0



Meets ASTM D-2564.

Gray

RECOMMENDED PIPE APPLICATION AND SIZES	SET-UP TIME (EVAPORATION RATE)		RECOMMENDED INSTALLATION TEMP.	LAP SHEAR @ 73°F	VISCOSITY AT 75° AS MANUFACTURED
Recommended for all grades and	10°-30°F	Not recommended	40° to 100°F	2 Hrs. 350 psi	500-900 cps
types of Carlon® wireway and fittings,	30°-50°F	5-6 minutes		16 Hrs. 800 psi	
except Flex-Plus® Blue™ ENT	50°-70°F	3-4 minutes		72 Hrs. 1,500 psi	
(Electrical Non-Metallic Tubing.)	70°_90°E	1_2 minutes			

Up through 6" diameter.

VOC emission of 490 grams/liter per the Bay and South Coast test method.

OAT NO	0175	APPLICATOR	DEGODIDATION	STD.	STD. WT.
CAT. NO.	SIZE	APPLICATOR	DESCRIPTION	CTN.	(LBS.)
VC9LV4-24	½ Pint	Dauber	Low VOC Gray	24	15.5
VC9LV3	Pint	Dauber	Low VOC Gray	24	27.0
VC9LV2	Quart	Dauber	Low VOC Gray	12	26.0
Meets ASTM D-2564.					





United States
Tel: 901.252.8000
800.816.7809

Fax: 901.252.1354

Technical Services Tel: 888.862.3289






Technical Information

Concrete Encasement Guidelines for Carlon® ENT

- 1. Cut ENT square and clean.
- 2. Insert end into fitting, making sure two (2) full corrugations are snapped into fitting beyond flexible tabs (2 clicks).
- **3.** ENT should be tied to rebar at 2–3 foot intervals to prevent flotation. Keep ENT straight. Small deflections over a long run may accumulate significant degrees of bend that will affect conductor installation. Suitable materials include wire, tie wraps and tape.
- When using rigid non-metallic conduit fittings for concrete tight performance:





- A. Do not use chemical primer or cleaner.
- Use a brush to apply a light, uniform coat of cement labeled for use with ENT on the coupling and ENT.
- C. Do not use a dauber.
- **D.** Brush excess cement out of ENT grooves.
- Promptly insert ENT into fitting while cement is wet, until the stop is reached, and give a quarter turn.
- F. Do not disturb until joint is set.

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

Specifications:

- 1.1 Electrical Non-Metallic Tubing (ENT) is designed to replace EMT, flexible metal conduit or other raceway or cable systems, for installation in accordance with Article 362 of the National Electrical Code® Section 12-1500 of the CEC, other applicable sections of the Code and local codes.
- 1.2 Any ENT used shall be listed to the requirements of UL® Standard UL 1653 in accordance with Article 362 of the NEC® and Section 12-1500 of the CEC.
- 1.3 Any ENT used shall meet the requirements of BI National Standard CAN/CSA-C22.2 No. 227.1-UL1653 and shall be Listed/Certified in accordance to the Electrical Codes.
- 1.4 Carlon's® ENT shall be installed per the technical assessment prepared by fire cause analysis for use in 1-hour and 2-hour rated construction.
- 1.5 Penetration of fire-rated walls, floors or ceilings shall use Classified Through-Penetration Firestop Systems described in the current Underwriters Laboratories Fire Resistance Directory
- 1.6 Fittings and outlet boxes designed for use with ENT shall be listed. All fittings, boxes and accessories shall be from one manufacturer.
- 1.7 Only Carlon® ENT Blue™ cement recommended specifically for use with ENT and rigid non-metallic fittings shall be used.
- 1.8 Unless indicated differently on drawings, ENT systems shall be color coded: BLUE for branch and feeder circuit wiring, YELLOW for communications and RED for fire alarm and emergency systems, or colors can designate different voltages.
- 1.9 ENT, fittings and accessories shall be manufactured by Carlon®.

Features:

- Recognized for use with PVC rigid non-metallic conduit fittings with all sizes of ENT
- ENT rated for 90° C conductors U.S., and 75° C Canada
- One-piece ENT Coupling, Threaded Terminator and RNC Transition Fitting are rated concrete tight without tape
- Recognized for use in 2-hour fire-resistive nonload-bearing and load-bearing wall assemblies
- Recognized for use in 1-hour fire-resistive nonload-bearing wall assemblies
- Recognized for use in a fire-resistive ceiling assembly (up to three hours)
- Recognized for Through-Penetration Firestop systems as classified by UL® to meet ICC building codes.
- Conductors easily push through the raceway (up to approximately 50 feet)
- For use in buildings in accordance with NEC® Article 362/CEC Section 12-1500
- **Outside Diameters meet IPS Dimensions**
- -4° F to 158° F Storage

-4° F to 104° F Handling

Continued on next page



United States

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

Technical Services Tel: 888.862.3289



Carlon[®]

Technical Information

Continued from previous page

Approved Uses:

- Concrete slab NEC® Article 362/CEC Section 12-1500
- Walls wood stud, masonry and metal stud NEC® Article 362/CEC Section 12-1500
- Ceilings permanent or dropped (free air only) NEC® Article 362/CEC Section 12-1500
- Exposed NEC® Article 362/CEC Section 12-1500
- Public assembly NEC® Section 518.4, in non-fire rated and certain fire rated structures
- Prewired NEC[®] Article 362/CEC Section 12-1500
- Classified by UL® 1479 for Through Penetration Firestop Systems in UL® Guide Category XHEZ and current UL Fire Resistance Directory
- Three-hour rated floor/ceiling assembly Raised floors NEC® Section 645.5(E)(2)
- Exposed or concealed in building above three floors when a fire sprinkler system is installed in accordance with NFPA 13 — NEC® Section 362.10(2)

- For use in residential attics up to three feet above the bottom of the ceiling joist
- Maximum ambient temperature 140° F (60° C)

Typical Applications:

- Residential: low or high rise multi or single family
- Commercial: low or high rise office, retail, hotel/motel, restaurant, etc.
- Nursing homes/hospitals in non-patient care areas only.
- · Schools, classrooms, dormitories, offices
- · Fire alarm systems
- Recreational vehicles and parks
- Solar photovoltaic systems
- Marinas and boatyards
- Other uses per the current NEC® and CEC

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

Carlon[®] Innerduct Guide When Innerduct is being used inside the building...

Plenum

- Must be UL[®] Listed
- Plenum cable must be installed
- Color: Industry-standard orange
- Pull tape pre-installed in sizes ½" through 3"

General Purpose and Riser

- Must be UL[®] Listed
- Riser-rated cable must be used in riser applications
- · Color: Industry-standard orange

	CARLON®
CAT. NO.	SIZE (IN.)
CD4X1C	1/2
CE4X1C	3/4
CF4X1C	1
CG4X1C	11/4
CH4X1C	1½
CJ4X1C	2
CL4X1C	3
	and the second s

PYF	RAMID®
CAT. NO.	SIZE (IN.)
PLM100T	1
PLM125T	11/4
PLM150T	11/2
PLM200T	2

CARLON®				
CAT. NO.	SIZE (IN.)			
DE4X1C	3/4			
DF4X1C	1			
DG4X1C	11/4			
DH4X1C	11/4			
DJ4X1C	2			
DL4X1C	3			

PYRAMID®				
CAT. NO.	SIZE (IN.)			
RIS100T	1			
RIS125T	11/4			
RIS150T	1½			
RIS200T	2			

Note: HDPE innerduct will not meet code

Specifying and installing UL® Listed innerducts with the anticipation of future upgrades provides the building owner with a low-cost solution for the removal of abandoned cables.



Tel: 888.862.3289





Catalog Number Index

CAT. NO.	PAGE NO.	CAT. NO.	PAGE NO.	CAT. NO.	PAGE NO.	CAT. NO.	PAGE NO.
255			5	A521DE		CE4X1C	
256		A220G	5	A5329DE	12	CE4X1C-1000	
257			5	A540DS		CF4X1-100S	
258			5	A58381D		CF4X1-100S	
259	25	A230D	5	A58381E	11	CF4X1-250	16
12005-200	4	A230E	5	A615D	13	CF4X1-250	18
12005-UPC	4	A230F	5	A615DE	13	CF4X1-250S	16
12005AK-001	4	A238	9	A615DH	13	CF4X1-250S	18
12005AKC-001	4	A238DIV	9	A615DJ	13	CF4X1C	30
12005C-370	4	A240D	10	A615DL	13	CF4X1C-100	16
12005R-200	4	A240E	10	A615E	13	CF4X1C-100	18
12005Y-200	4	A240F	10	A861	11	CF4X1C-1000	15
12007-100	4	A243D	10	A862D	11	CF4X1C-1500	15
12007-UPC	4	A243E	10	A862E	11	CF4X1C-250	16
12007AA-001	4	A243F	10	A863-4SQ	6	CF4X1C-250	18
12007C-240	4	A245D	8	A863-4SQF	6	CF4X1C-500	15
12007R-100	4	A245E	8	A863BC	6	CF4X1C-5200	15
12007Y-100	4	A245F	8	A863CF		CF4X1C-6500	15
12008-010	4		10	A863CFF	6	CF4X1C-8000	15
12008-100	4		10	A863CFG	6	CG4X1-200S	16
12008-750	4		10	A863CFGF		CG4X1-200S	18
12008C-160			8	A863D		CG4X1-500S	
12008C-750			8	A863DF		CG4X1-900S	
12008R-100			8	A863DG		CG4X1C	
12008R-750			8	A863DGF		CG4X1C-1600	
12008Y-100			8	A863MB		CG4X1C-200	
12008Y-750			7	A863S		CG4X1C-200	
12009-750			24	A863SF		CG4X1C-3200	
12010-750			24	A863SG		CG4X1C-500	
12010-750			24			CG4X1C-6500	
				A863SGF			
12011-500			12	A864D		CG4X1C-900	
12011R-500			12	A864E		CH4X1-150S	
12011Y-500			12	A864F		CH4X1-150S	
1205AKR-001		=	12	C861G		CH4X1C	
1205AKY-001			12	CC120B		CH4X1C-1200	
1207AAC-001			12	CC122	14	CH4X1C-150	
1207AAR-001		A420	12	CC125	14	CH4X1C-150	
1207AAY-001	4	A421	12	CD4X1C		CH4X1C-350	
A122	9	A422	12	CD4X1C-1500	15	CH4X1C-4000	15
A200D	5	A470D	13	CD4X1C-500	16	CJ4X1-100S	16
A200E	5	A471	13	CD4X1C-500	18	CJ4X1-100S	18
A200F	5	A472	13	CE4X1-1000	15	CJ4X1-200S	15
A210D	5	A52151D	11	CE4X1-1000S	15	CJ4X1C	
A210E	5	A52151E	11	CE4X1-350	16	CJ4X1C-100	16
A210F	5	A52171D	11	CE4X1-350	18	CJ4X1C-100	18
A220D	5	A52171E	11	CE4X1-350S	16	CJ4X1C-1400	15
A220E	5	A5217DE	11	CE4X1-350S	18	CJ4X1C-2000	15

Carlon[®]

Catalog Number Index

CAT. NO.	PAGE NO.	CAT. NO.	PAGE NO.	CAT. NO.	PAGE NO.
CJ4X1C-225	15	E940G	10	PLM100T-8000	20
CJ4X1C-2800	15	E940G	25	PLM125T	30
CJ4X1C-700	15	E940H	10	PLM125T-1000	20
CL4X1C	30	E940H	25	PLM125T-250B4	20
CL4X1C-150	15	E940J	10	PLM125T-500	20
DE4X1-1000	17	E940J	25	PLM125T-5000	20
DE4X1C	30	E943D	10	PLM125T-6000	20
DF4X1C	30	E943E	10	PLM150T	30
DF4X1C-1000	17	E943E	25	PLM150T-2000	20
DF4X1C-1500	17	E943EW	25	PLM150T-4000	20
DF4X1C-2700	17	E943F	10	PLM200T	30
DF4X1C-500R	17	E943F	25	PLM200T-2000	20
DF4X1C-5200	17	E943FW	25	RHF100T-5000	21
DF4X1C-6500	17	E943G	10	RHF125T-4000	
DF4X1C-7000	17	E943G	25	RHF150T-2000	21
DF4X1C-9400	17	E943GW	25	RHF200T-2000	21
DG4X1C	30	E943H	10	RIS100T	30
DG4X1C-1500	17	E943H	25	RIS100T-5000	21
DG4X1C-1600	17	E943HW	25	RIS125T	
DG4X1C-3200	17	E943J	10	RIS125T-4000	
DG4X1C-4500		E943J		RIS150T	
DG4X1C-500R		E943JW		RIS150T-2000	
DG4X1C-5600		HF4X4C-5000		RIS200T	
DG4X1C-6500		HG4X4C-4000		RIS200T-2000	
DG4X1C-900		HH4X4C-2000		SC100A	·····-
DH4X1C		HJ4X4C-2000		SC100ADJC	
DH4X1C-1200		MGP08MT-1000		SC100SC	
DH4X1C-4000		MGP08MT-2500		SC200A	
DH4X1C-4500		MGP08MT-5000		SC200ADJC	
DJ4X1C		MGP08RMT		SC200DV	
DJ4X1C-2000		MGP12MT-1000		SC300A	
DJ4X1C-2800		MGP12MT-2500		SCA240F	
DJ4X1C-700		MGP12MT-5000		SCA240F	·····-
DL4X1C		MGP12RMT		SCA243E	
DL4X1C-750		MGR08JT-1000		SCA243F	
E460R-CAR		MGR08JT-2500		SCA253E	
E92CSH		MGR08JT-5000		SCA253F	
E92CSJ		MGR08RJT		SCE940G	
E92CSL		MGR12JT-1000		SCE940H	
E92CSN		MGR12JT-2500		SCE940J	
E92CSP		MGR12JT-5000		SCE943G	
E92CSR		MGR12RJT		SCE943H	
E940D		PLM100T		SCE943J	
E940E		PLM100T-1800		TL14505	
E940E		PLM100T-1600		TL14510	
E940F		PLM100T-500B2		TL38203	
E940F		PLM100T-500		TL38210	
L34UF	20	rLIVI1001-3000	20	1L30210	14

CAT. NO.	PAGE NO.
TL38265	14
VC9961P	27
VC9962	27
VC9963	27
VC9964	27
VC9981P	28
VC9982	28
VC9983	28
VC9984	28
VC9992	14
VC9LV2	28
VC9LV3	28
VC9LV4-24	28



A Global Leader in Innovative...

Wire & Cable Management

Carlon Catamount **EZCODE** Kindorf rededot. Steel City Superstrut T&B Cable Tray Ty-Duct Ty-Rap



Cable Protection Systems

Adaptafleri Carlon' <u>Harnessflex</u> **KOPEX-EX** Ocal'

PMA' rededet. Steel City: T&B' Fittings



Power Connection & Control

Blackburn Compression **Blackburn** Grounding **Blackburn** Mechanical





Safety Technology









Visit our world of electrical product solutions

Visit the "Electrical World" section of our web site at **www.tnb.com** for more information on Thomas & Betts solutions including our newest products, plus user-friendly catalog and competitive part number search, application and technical support and other useful information. Click on the Electrical World icon or go to: **tnbelectricalworld.tnb.com**.

Industry codes and specifications

Thomas & Betts products meet or exceed applicable industry specifications or codes which are detailed in the appropriate T&B product literature.







Online CAD library

Thomas & Betts offers free download of two- and threedimensional CAD models of many of its products in more than 90 native CAD formats at: www.tnb.com/cadlibrary

Thomas & Betts Corporation

8155 T&B Boulevard Memphis, TN 38125 901,252.8000

www.tnb.com

United States

Thomas & Betts Corporation
Electrical Division Headquarters
8155 T&B Boulevard
Memphis, TN 38125
Phone: 901.252.8000
Fax: 800.816.7810
Technical Services:
888.862.3289
Email: techsupport@tnb.com

Canada

Thomas & Betts Ltd 700 Thomas Avenue Saint-Jean-sur-Richelieu, Quebec J2X 2M9

Phone: 450.347.5318 Fax: 450.347.1976

Latin America

Mexico: 01-800-TNB-HELP Central America & Caribbean: +52.81.8329.7707 South America: +52.81.8329.7743

Email: servicioalcliente@tnb.com

Europe/Africa

T&B European Centre 200 Chaussée de Waterloo B-1640 Rhode-St-Genèse Belgium

Phone: +32.235.98200

Email: europe_inquiry@tnb.com

Middle East

Thomas & Betts Ltd PO Box 54567 Dubai Airport Free Zone Bldg. 6WA Suite 724 Dubai United Arab Emirates Phone: +9714 6091635 Fax: +9714 6091636

Asia Pacific

Thomas & Betts Asia Pte Ltd 10 Ang Mo Kio Street 65 #06-07 Techpoint Singapore 569059 Phone: +65.6720.8828 Fax: +65.6720.8780 Email: asia_inquiry@tnb.com

American Recovery and Reinvestment Act (ARRA)



Get certification letters for compliant products online at:

www.tnb.com/ARRA

