



- No Need To Buy A New Bit When Just The Tip Is Worn
- A Real Money Saver. Base Bits Last 3 to 4 Times Longer At A Fraction Of The Cost
- Economical Replaceable-Tips Lock In Place.
- Step Bit Performance Remains Identical To That Of Non-Replaceable Tip Bits.
- Constructed Of M2 High Speed Steel, Coated With Titanium And Cobalt.
- Tri-Cut Tip Cuts Smoother, Faster And Cooler.

# The TIP-BITS™

The new Dottie Tip-Bits are step drill bits with a replaceable tip. Rather than throwing away a good bit that just won't start a hole, the first few steps can be replaced making the drill bit start like new again.



TOOLS & SPECIALTY ITEMS > TIP-BITS

| CAT NO   | UPC   | SIZE RANGE   | SHANK | STD | MSTR | WT/STD | UNIT |
|----------|-------|--|-------|-----|------|--------|------|
| RTTP6000 | 81210 | Replaceable Tip - 2 Pack<br>Fits all Tip Bits.<br>Can also be used as a 1/4" - 1/2" Step Drill<br>Steps: 5/32", 1/4", 5/16", 3/8", 7/16", 1/2" | 1/4"  | 1   | 15   | 0.10#  | Ea   |
| RTTP6010 | 81211 | 1/4" - 7/8" Base & Tip<br>Steps: 9/16", 11/16", 3/4", 13/16", 7/8"   | 1/4"  | 1   | 5    | 0.20#  | Ea   |
| RTTP6020 | 81212 | 1/4" - 1-1/8" Base & Tip<br>Steps: 19/32", 21/32", 3/4", 13/16", 7/8", 15/16", 1-1/32", 1-1/18"  | 1/4"  | 1   | 5    | 0.30#  | Ea   |
| RTTP6030 | 81213 | 1/4" - 1-3/8" Base & Tip<br>Steps: 5/8", 3/4", 7/8", 1", 1-1/16", 1-3/16", 1-1/4", 1-5/16", 1-3/8"   | 1/4"  | 1   | 5    | 0.50#  | Ea   |
| RTTP6040 | 81214 | Kit contains:<br>1/4" - 1/2" Extra Tip<br>1/4" - 7/8" Base & Tip<br>1/4" - 1-1/8" Base & Tip   | 1/4"  | 1   | 4    | 0.55#  | Ea   |



## Drill/Tap/Countersink Hex Bit Kit PC 6348



- Drill, Tap And Deburr In One Operation
- One-Piece Construction Guarantees Drill For Tap Size
- Made From High Speed M2 Steel
- Tapered Tap Prevents Thread Damage From Over-drilling
- Countersink Also Provided On Bit Beyond Back Taper
- 135° Self-Centering Split Point Tip
- Designed To Tap Up To 10 Gauge Metal
- 6 Piece Bit Set Includes: 6-32", 8-32", 10-24", 10-32", 12-24", 1/4"
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION                       | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------------|-----|------|--------|------|
| DRT6C  | 12870 | Drill/Tap/Countersink Hex Bit Kit | 1   | 10   | 0.30#  | Ea   |

### Replacement Bits

|          |       |                        |   |    |        |    |
|----------|-------|------------------------|---|----|--------|----|
| DT632NC  | 12880 | 6-32 Drill & Tap Bit   | 1 | 10 | 0.020# | Ea |
| DT832NC  | 12881 | 8-32 Drill & Tap Bit   | 1 | 10 | 0.020# | Ea |
| DT1024NC | 12882 | 10-24 Drill & Tap Bit  | 1 | 10 | 0.020# | Ea |
| DT1032NF | 12900 | 10-32 Drill & Tap Bit  | 1 | 10 | 0.020# | Ea |
| DT1224NC | 12884 | 12-24 Drill & Tap Bit  | 1 | 10 | 0.020# | Ea |
| DT1420NC | 12885 | 1/4-20 Drill & Tap Bit | 1 | 10 | 0.020# | Ea |



## ProGrabit - Screw Removal Kit PC 6352

ProGrabit works on damaged screws and broken bolts from as small as a No. 4 screw to as large as a 3/8 in. bolt.

- Quickly And Easily Removes Most Damaged Screws Such As Hex, Phillips, Torx, Square Drive; Sizes No. 4 - No.14 From Wood, Plastic Or Metal
- Two-Step, Drill Bit And Extractor In One Tool Extracts Broken Bolts And Damaged Screws Fast
- Use In Reverse Only With 3/8 In. Variable Speed Reversible Power Drill
- Drills Up To Grade 8 And 10.0 Class Fasteners; Extracts Bolt Sizes No. 10-3/8 In. (5mm-10mm)

| CAT NO | UPC   | DESCRIPTION                         | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------------------------|-----|------|--------|------|
| GBKP   | 81967 | 3-Piece ProGrabit Screw Removal Kit | 1   | 10   | 0.20#  | Ea   |

### Replacement Bits

|         |       |                                   |   |    |       |    |
|---------|-------|-----------------------------------|---|----|-------|----|
| GB47R   | 81968 | #4-#7 ProGrabit Replacement Bit   | 1 | 10 | 0.05# | Ea |
| GB610R  | 81969 | #6-#10 ProGrabit Replacement Bit  | 1 | 10 | 0.05# | Ea |
| GB1214R | 81970 | #12-#14 ProGrabit Replacement Bit | 1 | 10 | 0.05# | Ea |



## Nylon Screw Starter PC 6620

The nylon screw starter grips a slotted screw positively and is ideal for starting and removing screws in awkward or inaccessible places. The unit releases when the applied torque reaches the proper level.

- Nonconductive Handle
- Releases When Tightened

| CAT NO | UPC   | DESCRIPTION            | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------------|-----|------|--------|------|
| NH6    | 28600 | 6" Nylon Screw Starter | 1   | 12   | 0.050# | Ea   |
| NH9    | 28610 | 9" Nylon Screw Starter | 1   | 12   | 0.060# | Ea   |



# High Speed Steel Drills & Sets PC 6350



- Industrial Quality
- M2 High Speed Steel
- Heavy Duty Jobber Length
- Fractional Sizes
- 3 Flats on Sizes 3/16" and Larger
- Black and Gold Finish
- Caution! Always Wear Eye Protection

High speed drills are rolled forged and have a 135° split point. They are suitable for steel, steel forging, cast iron and other work materials.

| CAT NO                                       | UPC   | SIZE   | DECIMAL | LENGTH | STD | MSTR | WT/STD | UNIT |
|--|-------|--------|---------|--------|-----|------|--------|------|
| <b>High Speed Drills / Heavy Duty Jobber</b> |       |        |         |        |     |      |        |      |
| HS4  | 29304 | 1/16"  | .0625   | 1-7/8" | 12  | 12   | .030#  | Ea   |
| HS5  | 29305 | 5/64"  | .0781   | 2"     | 12  | 12   | .040#  | Ea   |
| HS6  | 29306 | 3/32"  | .0938   | 2-1/4" | 12  | 12   | .050#  | Ea   |
| HS7  | 29307 | 7/64"  | .1094   | 2-5/8" | 12  | 12   | .070#  | Ea   |
| HS8  | 29308 | 1/8"   | .1250   | 2-3/4" | 12  | 12   | .090#  | Ea   |
| HS9  | 29309 | 9/64"  | .1406   | 2-7/8" | 12  | 12   | .110#  | Ea   |
| HS10   | 29310 | 5/32"  | .1562   | 3-1/8" | 12  | 12   | .140#  | Ea   |
| HS11   | 29311 | 11/64" | .1719   | 3-1/4" | 12  | 12   | .190#  | Ea   |
| HS12   | 29312 | 3/16"  | .1875   | 3-1/2" | 12  | 12   | .240#  | Ea   |
| HS13   | 29313 | 13/64" | .2031   | 3-5/8" | 12  | 12   | .270#  | Ea   |
| HS14   | 29314 | 7/32"  | .2188   | 3-3/4" | 12  | 12   | .320#  | Ea   |
| HS15   | 29315 | 15/64" | .2344   | 3-7/8" | 12  | 12   | .370#  | Ea   |
| HS16   | 29316 | 1/4"   | .2500   | 4"     | 12  | 12   | .440#  | Ea   |
| HS17   | 29317 | 17/64" | .2656   | 4-1/8" | 12  | 12   | .740#  | Ea   |
| HS18   | 29318 | 9/32"  | .2812   | 4-1/4" | 12  | 12   | .570#  | Ea   |
| HS19   | 29319 | 19/64" | .2969   | 4-3/8" | 12  | 12   | .630#  | Ea   |
| HS20   | 29320 | 5/16"  | .3125   | 4-1/2" | 12  | 12   | .740#  | Ea   |
| HS21   | 29321 | 21/64" | .3281   | 4-5/8" | 6   | 6    | .440#  | Ea   |
| HS22   | 29322 | 11/32" | .3438   | 4-3/4" | 6   | 6    | .510#  | Ea   |
| HS23   | 29323 | 23/64" | .3594   | 4-7/8" | 6   | 6    | .530#  | Ea   |
| HS24   | 29324 | 3/8"   | .3750   | 5"     | 6   | 6    | .640#  | Ea   |
| HS25   | 29325 | 25/64" | .3906   | 5-1/8" | 6   | 6    | .660#  | Ea   |
| HS26   | 29326 | 13/32" | .4062   | 5-1/4" | 6   | 6    | .690#  | Ea   |
| HS27   | 29327 | 27/64" | .4219   | 5-3/8" | 6   | 6    | .820#  | Ea   |
| HS28   | 29328 | 7/16"  | .4375   | 5-1/2" | 6   | 6    | .890#  | Ea   |
| HS29   | 29329 | 29/64" | .4531   | 5-5/8" | 6   | 6    | .930#  | Ea   |
| HS30   | 29330 | 15/32" | .4688   | 5-3/4" | 6   | 6    | 1.000# | Ea   |
| HS31   | 29331 | 31/64" | .4844   | 5-7/8" | 6   | 6    | 1.090# | Ea   |
| HS32   | 29332 | 1/2"   | .5000   | 6"     | 6   | 6    | 1.150# | Ea   |

### High Speed Drill Bit Merchandiser (252D)

Our attractive counter top High Speed Drill Merchandiser has been one of the most popular selling tools in our distributors showrooms for many years. When fully stocked our display offers a wide assortment of the most popular high speed drills to satisfy the needs of every contractor. The clear acrylic lockable lid allows for easy viewing of the product with out the concern of shrinkage.

252D



### High Speed Steel Drill Sets PC 6330

- Industrial Quality
- M2 High Speed Steel
- Heavy Duty Jobber Length
- Fractional Sizes
- 3 Flats on Sizes 3/16" and Larger
- Black and Gold Finish
- Caution! Always Wear Eye Protection

High speed drills are rolled forged and have a 135° split point. They are suitable for steel, steel forging, cast iron and other work materials.



| CAT NO | UPC   | DESCRIPTION | SIZES             | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|-------------------|-----|------|--------|------|
| M213   | 66500 | 13 pc. set  | 1/16"-1/4" x 64th | 1   | 10   | 0.710# | Ea   |
| M221   | 66550 | 21 pc. set  | 1/16"-3/8" x 64th | 1   | 10   | 1.580# | Ea   |
| M229   | 29850 | 29 pc. set  | 1/16"-1/2" x 64th | 1   | 10   | 3.100# | Ea   |


### Dial-A-Drill PC 6340

- Industrial Quality
- M2 High Speed Steel
- Jobber Length
- Fractional Sizes
- Caution! Always Wear Eye Protection



| CAT NO | UPC   | DESCRIPTION | SIZES             | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|-------------------|-----|------|--------|------|
| DB13K  | 67510 | 13 pc. set  | 1/16"-1/4" x 64th | 1   | 10   | 0.320# | Ea   |

See new products at [Ihdottie.com](http://Ihdottie.com)



TOOLS & SPECIALTY ITEMS > HIGH SPEED DRILLS & SETS > DIAL-A-DRILL

## Carbide Tip Masonry Drill Bits PC 6320

Masonry drills have tungsten carbide tips and are suitable for brick, concrete, tile, slate and cinder block.

- Tungsten Carbide
- Tempered Body For Long Life
- Slow Spiral
- Suitable For Rotary Or Percussion
- Black Oxide Coated
- One Per Display Pouch
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | SIZE      | SHANK | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|-------|-----|------|--------|------|
| MD1    | 30205 | 3/16 x 4" | 3/16" | 1   | 10   | 0.030# | Ea   |
| MD2    | 30210 | 1/4 x 4"  | 1/4"  | 1   | 10   | 0.040# | Ea   |
| MD2L   | 30300 | 1/4 x 6"  | 1/4"  | 1   | 5    | 0.070# | Ea   |
| MD2XL  | 30302 | 1/4 x 12" | 1/4"  | 1   | 5    | 0.150# | Ea   |
| MD3    | 30215 | 5/16 x 4" | 1/4"  | 1   | 10   | 0.060# | Ea   |
| MD4    | 30220 | 3/8 x 4"  | 1/4"  | 1   | 10   | 0.070# | Ea   |
| MD4L   | 30304 | 3/8 x 6"  | 1/4"  | 1   | 5    | 0.130# | Ea   |
| MD4XL  | 30306 | 3/8 x 12" | 3/8"  | 1   | 5    | 0.290# | Ea   |
| MD5    | 30225 | 7/16 x 4" | 1/4"  | 1   | 5    | 0.100# | Ea   |
| MD6    | 30230 | 1/2 x 4"  | 1/4"  | 1   | 5    | 0.110# | Ea   |
| MD6L   | 30308 | 1/2 x 6"  | 1/4"  | 1   | 5    | 0.210# | Ea   |
| MD6XL  | 30310 | 1/2 x 12" | 3/8"  | 1   | 5    | 0.450# | Ea   |
| MD7L   | 30312 | 5/8 x 6"  | 3/8"  | 1   | 5    | 0.290# | Ea   |
| MD7XL  | 30314 | 5/8 x 12" | 3/8"  | 1   | 1    | 0.580# | Ea   |
| MD8L   | 30316 | 3/4 x 6"  | 1/2"  | 1   | 1    | 0.440# | Ea   |
| MD8XL  | 30318 | 3/4 x 12" | 1/2"  | 1   | 1    | 0.920# | Ea   |
| MD9L   | 30320 | 7/8 x 6"  | 1/2"  | 1   | 1    | 0.560# | Ea   |
| MD10L  | 30322 | 1 x 6"    | 1/2"  | 1   | 1    | 0.710# | Ea   |

## SDS 4 Plus Rotary Hammer Drill Bits PC 4580

This fast, tough carbide tip provides long life, easy centering, and fast drilling through all aggregates, concrete, masonry, brick, stone and even rebar! A dynamic chisel-shaped drill head ensures swift penetration and feeds the debris simultaneously to the flute section. The 3 fluted, spacious KVS-spiral removes the debris rapidly from the bore hole, saving the operator both time and money.

- Cuts Through Rebar
- Easy Centering
- Special Flute Design
- Conforms To ANSI Standards
- Special Tungsten Carbide Tip
- Caution! Always Wear Eye Protection

| CAT NO    | UPC   | SIZE          | DRILLING DEPTH | STD | MSTR | WT/STD | UNIT |
|-----------|-------|---------------|----------------|-----|------|--------|------|
| SDS36412  | 12200 | 3/16 x 4-1/2" | 2"             | 1   | 6    | 0.082# | Ea   |
| SDS36614  | 12201 | 3/16 x 6-1/4" | 4"             | 1   | 6    | 0.088# | Ea   |
| SDS36814  | 12202 | 3/16 x 8-1/4" | 6"             | 1   | 6    | 0.100# | Ea   |
| SDS3610   | 12203 | 3/16 x 10"    | 8"             | 1   | 6    | 0.130# | Ea   |
| SDS3612   | 12204 | 3/16 x 12"    | 10"            | 1   | 6    | 0.150# | Ea   |
| SDS732412 | 12205 | 7/32 x 4-1/2" | 2"             | 1   | 6    | 0.100# | Ea   |
| SDS732614 | 12206 | 7/32 x 6-1/4" | 4"             | 1   | 6    | 0.120# | Ea   |
| SDS732814 | 12207 | 7/32 x 8-1/4" | 6"             | 1   | 6    | 0.130# | Ea   |
| SDS14412  | 12208 | 1/4 x 4-1/2"  | 2"             | 1   | 6    | 0.100# | Ea   |
| SDS14614  | 12209 | 1/4 x 6-1/4"  | 4"             | 1   | 6    | 0.106# | Ea   |
| SDS14814  | 12210 | 1/4 x 8-1/4"  | 6"             | 1   | 6    | 0.136# | Ea   |
| SDS1411   | 12211 | 1/4 x 11"     | 9"             | 1   | 6    | 0.160# | Ea   |
| SDS1414   | 12212 | 1/4 x 14"     | 12"            | 1   | 6    | 0.190# | Ea   |
| SDS516614 | 12213 | 5/16 x 6-1/4" | 4"             | 1   | 6    | 0.126# | Ea   |
| SDS516814 | 12214 | 5/16 x 8-1/4" | 6"             | 1   | 6    | 0.150# | Ea   |
| SDS38614  | 12215 | 3/8 x 6-1/4"  | 4"             | 1   | 6    | 0.156# | Ea   |
| SDS38814  | 12216 | 3/8 x 8-1/4"  | 6"             | 1   | 6    | 0.192# | Ea   |
| SDS381014 | 12217 | 3/8 x 10-1/4" | 8"             | 1   | 6    | 0.230# | Ea   |
| SDS381214 | 12218 | 3/8 x 12-1/4" | 10"            | 1   | 6    | 0.294# | Ea   |
| SDS3818   | 12219 | 3/8 x 18"     | 16"            | 1   | 6    | 0.500# | Ea   |
| SDS12614  | 12220 | 1/2 x 6-1/4"  | 4"             | 1   | 6    | 0.194# | Ea   |
| SDS121014 | 12221 | 1/2 x 10-1/4" | 8"             | 1   | 6    | 0.276# | Ea   |
| SDS121214 | 12222 | 1/2 x 12-1/4" | 10"            | 1   | 6    | 0.406# | Ea   |
| SDS1218   | 12223 | 1/2 x 18"     | 16"            | 1   | 6    | 0.700# | Ea   |
| SDS58614  | 12224 | 5/8 x 6-1/4"  | 4"             | 1   | 6    | 0.220# | Ea   |
| SDS588    | 12225 | 5/8 x 8"      | 6"             | 1   | 6    | 0.280# | Ea   |
| SDS5812   | 12226 | 5/8 x 12"     | 10"            | 1   | 6    | 0.500# | Ea   |
| SDS5818   | 12227 | 5/8 x 18"     | 16"            | 1   | 6    | 0.800# | Ea   |
| SDS349    | 12228 | 3/4 x 9"      | 6"             | 1   | 6    | 0.466# | Ea   |
| SDS789    | 12229 | 7/8 x 9"      | 6"             | 1   | 6    | 0.540# | Ea   |



## Ship Augers PC 6290



- Heat Treated For Long Life
- Self Feeding Screw Point
- 7/16" Hex Shank
- Packed In Display Pouch
- 2 Recesses Provided for Extensions
- Caution! Always Wear Eye Protection

Ship augers are versatile, high quality drills with a self feed screw point for fast, effortless boring and quick chip removal. Designed for drilling through clean lumber or wood where small nails may be encountered.

| CAT NO | UPC   | SIZE   | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----|------|--------|------|
| 609    | 14609 | 9/16"  | 1   | 6    | 0.290# | Ea   |
| 610    | 14610 | 5/8"   | 1   | 6    | 0.340# | Ea   |
| 612    | 14612 | 3/4"   | 1   | 6    | 0.390# | Ea   |
| 613    | 14613 | 13/16" | 1   | 6    | 0.490# | Ea   |
| 614    | 14614 | 7/8"   | 1   | 6    | 0.490# | Ea   |
| 615    | 14615 | 15/16" | 1   | 6    | 0.510# | Ea   |
| 616    | 14616 | 1"     | 1   | 6    | 0.570# | Ea   |
| 618    | 14618 | 1-1/8" | 1   | 6    | 0.690# | Ea   |
| 620    | 14620 | 1-1/4" | 1   | 6    | 0.800# | Ea   |
| 622    | 14622 | 1-3/8" | 1   | 6    | 0.900# | Ea   |
| 624    | 14624 | 1-1/2" | 1   | 6    | 1.010# | Ea   |
| <hr/>  |       |        |     |      |        |      |
| 1809   | 21809 | 9/16"  | 1   | 6    | 0.750# | Ea   |
| 1810   | 21810 | 5/8"   | 1   | 6    | 0.810# | Ea   |
| 1812   | 21812 | 3/4"   | 1   | 6    | 0.990# | Ea   |
| 1813   | 21813 | 13/16" | 1   | 6    | 1.170# | Ea   |
| 1814   | 21814 | 7/8"   | 1   | 6    | 1.170# | Ea   |
| 1815   | 21815 | 15/16" | 1   | 6    | 1.210# | Ea   |
| 1816   | 21816 | 1"     | 1   | 6    | 1.400# | Ea   |
| 1818   | 21818 | 1-1/8" | 1   | 6    | 1.660# | Ea   |
| 1820   | 21820 | 1-1/4" | 1   | 6    | 2.050# | Ea   |
| 1822   | 21822 | 1-3/8" | 1   | 6    | 2.280# | Ea   |
| 1824   | 21824 | 1-1/2" | 1   | 6    | 2.610# | Ea   |

## Ship Auger & Speed D Feed Extensions PC 6310



- Forged From High Grade Steel
- Accommodates 7/16" Diameter Shanks
- Add 5-1/2" to 24" In Length
- Heavy Duty Double Set Screw Lock

Extensions are used where additional reach is required.

| CAT NO | UPC   | LENGTH | SHANK DIA | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------|-----------|-----|------|--------|------|
| X5     | 21955 | 5-1/2" | 7/16"     | 1   | 6    | 0.500# | Ea   |
| X9     | 22009 | 9"     | 7/16"     | 1   | 6    | 0.690# | Ea   |
| X12    | 21956 | 12"    | 7/16"     | 1   | 6    | 0.950# | Ea   |
| X18    | 22018 | 18"    | 7/16"     | 1   | 6    | 1.200# | Ea   |
| X24    | 22024 | 24"    | 7/16"     | 1   | 6    | 1.460# | Ea   |

## Auger Bit File PC 6291



- Professional Grade
- Caution! Always Wear Eye Protection

Specially designed to sharpen auger bits for longer cutting life.

| CAT NO | UPC   | DESCRIPTION       | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------|-----|------|--------|------|
| AF7    | 11630 | 7" Auger Bit File | 1   | 6    | 0.040# | Ea   |



## Spade Drill Bits PC 6270

Spade drills are used for boring hardwoods, softwood, plywood and drywall. Fully heat treated to extend bit life and individually stamped with size.

- Cold Forged
- Machine Finish Cutting Groove
- Rust Protection
- Wing Tip Design
- Precision Ground Hex Shank
- Caution! Always Wear Eye Protection

| CAT NO                           | UPC   | SIZE   | LENGTH | STD | MSTR | WT/STD | UNIT |
|----------------------------------|-------|--------|--------|-----|------|--------|------|
| <b>Packed in a Hanging Pouch</b> |       |        |        |     |      |        |      |
| SPD14                            | 21700 | 1/4"   | 6"     | 1   | 6    | 0.060# | Ea   |
| SPD516                           | 21702 | 5/16"  | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD38                            | 21704 | 3/8"   | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD716                           | 21706 | 7/16"  | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD12                            | 21708 | 1/2"   | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD916                           | 21710 | 9/16"  | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD58                            | 21712 | 5/8"   | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD1116                          | 21714 | 11/16" | 6"     | 1   | 6    | 0.110# | Ea   |
| SPD34                            | 21716 | 3/4"   | 6"     | 1   | 6    | 0.110# | Ea   |
| SPD1316                          | 21718 | 13/16" | 6"     | 1   | 6    | 0.100# | Ea   |
| SPD78                            | 21720 | 7/8"   | 6"     | 1   | 6    | 0.110# | Ea   |
| SPD1516                          | 21722 | 15/16" | 6"     | 1   | 6    | 0.120# | Ea   |
| SPD1                             | 21724 | 1"     | 6"     | 1   | 6    | 0.110# | Ea   |
| SPD118                           | 21726 | 1-1/8" | 6"     | 1   | 6    | 0.130# | Ea   |
| SPD114                           | 21728 | 1-1/4" | 6"     | 1   | 6    | 0.130# | Ea   |
| SPD138                           | 21730 | 1-3/8" | 6"     | 1   | 6    | 0.140# | Ea   |
| SPD112                           | 21732 | 1-1/2" | 6"     | 1   | 6    | 0.150# | Ea   |



## Bell Hanger Drills PC 6280

Bell hanger drills are used to drill and fish small gauge wires. After drilling through the stud or header, a wire is attached to the fish hole in the flute and the drill is retracted, pulling the wire through. Bell hangers are available in a variety of diameters and lengths and are suitable for telephone installations, security and cable applications.


- Fish Hole In Flute For Pulling Wire
- Tapered For Quick Chip Clearance
- One Per Display Pouch
- Aggressive Point For Fast Drilling In Wood & Metal
- Caution! Always Wear Eye Protection

| CAT NO                           | UPC   | SIZE  | LENGTH | STD | MSTR | WT/STD | UNIT |
|----------------------------------|-------|-------|--------|-----|------|--------|------|
| <b>Packed in a Hanging Pouch</b> |       |       |        |     |      |        |      |
| BLH3612                          | 21750 | 3/16" | 12"    | 1   | 6    | 0.110# | Ea   |
| BLH1412                          | 21752 | 1/4"  | 12"    | 1   | 6    | 0.170# | Ea   |
| BLH5612                          | 21754 | 5/16" | 12"    | 1   | 6    | 0.250# | Ea   |
| BLH3812                          | 21756 | 3/8"  | 12"    | 1   | 6    | 0.340# | Ea   |
| BLH1212                          | 21758 | 1/2"  | 12"    | 1   | 6    | 0.540# | Ea   |
| BLH1418                          | 21760 | 1/4"  | 18"    | 1   | 6    | 0.260# | Ea   |
| BLH5618                          | 21762 | 5/16" | 18"    | 1   | 6    | 0.390# | Ea   |
| BLH3818                          | 21764 | 3/8"  | 18"    | 1   | 6    | 0.550# | Ea   |
| BLH1218                          | 21766 | 1/2"  | 18"    | 1   | 6    | 0.870# | Ea   |
| BLH1424                          | 21770 | 1/4"  | 24"    | 1   | 6    | 0.350# | Ea   |
| BLH5624                          | 21772 | 5/16" | 24"    | 1   | 6    | 0.530# | Ea   |
| BLH3824                          | 21774 | 3/8"  | 24"    | 1   | 6    | 0.750# | Ea   |
| BLH1224                          | 21776 | 1/2"  | 24"    | 1   | 6    | 1.220# | Ea   |
| BLH1430                          | 21778 | 1/4"  | 30"    | 1   | 6    | 0.380# | Ea   |
| BLH3830                          | 21780 | 3/8"  | 30"    | 1   | 6    | 0.880# | Ea   |
| BLH1442                          | 21782 | 1/4"  | 42"    | 1   | 6    | 0.610# | Ea   |
| BLH3842                          | 21784 | 3/8"  | 42"    | 1   | 6    | 1.310# | Ea   |

## TECH TALK



Electrician's Flex-A-Bits are specifically designed to facilitate fishing wires and cables through walls and ceilings. A self feeding screw point is permanently brazed to flexible shafts.



## Speed D Feed Bits PC 6355



- Fast Heavy Duty Power Boring
- Tapered Back For Easy Back Out
- Universal 7/16" Shank, 5" OA Length
- Replaceable Double Ended Self Feeding Point
- Open Design For No Clog Fast Chip Removal
- Precision Angled Surface For Smoother Cuts
- Caution! Always Wear Eye Protection

Speed D Feed multi-spur wood boring bits are ideal for boring large holes quickly - from 1" through 4-5/8". This bit is especially suited to electricians and plumbers.

| CAT NO  | UPC   | SIZE    | STD | MSTR | WT/STD | UNIT |
|---------|-------|---------|-----|------|--------|------|
| SDF100  | 21900 | 1"      | 1   | 6    | 0.438# | Ea   |
| SDF118  | 21901 | 1-1/8"  | 1   | 6    | 0.469# | Ea   |
| SDF114  | 21902 | 1-1/4"  | 1   | 6    | 0.500# | Ea   |
| SDF138  | 21903 | 1-3/8"  | 1   | 6    | 0.500# | Ea   |
| SDF112  | 21904 | 1-1/2"  | 1   | 6    | 0.563# | Ea   |
| SDF134  | 21905 | 1-3/4"  | 1   | 6    | 0.625# | Ea   |
| SDF200  | 21906 | 2"      | 1   | 6    | 0.719# | Ea   |
| SDF218  | 21907 | 2-1/8"  | 1   | 6    | 0.813# | Ea   |
| SDF214  | 21908 | 2-1/4"  | 1   | 6    | 0.938# | Ea   |
| SDF2916 | 21909 | 2-9/16" | 1   | 6    | 1.063# | Ea   |
| SDF300  | 21910 | 3"      | 1   | 6    | 1.500# | Ea   |
| SDF358  | 21911 | 3-5/8"  | 1   | 6    | 2.000# | Ea   |
| SDF458  | 21912 | 4-5/8"  | 1   | 6    | 3.500# | Ea   |

### Replacement Screw Points

|        |       |                                       |   |   |       |    |
|--------|-------|---------------------------------------|---|---|-------|----|
| SDF14S | 21913 | 1/4 x 2-1/2"<br>(For 1" thru 2-9/16") | 1 | 6 | 0.01# | Ea |
| SDF14L | 21914 | 1/4 x 2-3/4"<br>(For 3" thru 4-5/8")  | 1 | 6 | 0.01# | Ea |

## Flex-A-Bit PC 6360



- Self Feeding Point
- Flexible Spring Steel Shaft
- Display Pack
- Caution! Always Wear Eye Protection

Flex A Bits are used to drill within walls and are able to reach normally inaccessible areas through a small opening. After (drilling) through a stud or header, a wire is attached to the fish hole in the flute and the drill is retracted pulling the wire through. The FG357 Flex A Guide tool aids in positioning the bit.

| CAT NO | UPC   | SIZE       | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------|-----|------|--------|------|
| FB3854 | 37000 | 3/8 x 54"  | 1   | 6    | 0.500# | Ea   |
| FB3872 | 37005 | 3/8 x 72"  | 1   | 6    | 0.640# | Ea   |
| FB5054 | 37010 | 1/2 x 54"  | 1   | 6    | 0.530# | Ea   |
| FB5072 | 37015 | 1/2 x 72"  | 1   | 6    | 0.680# | Ea   |
| FB9654 | 37030 | 9/16 x 54" | 1   | 6    | 0.540# | Ea   |
| FB9672 | 37035 | 9/16 x 72" | 1   | 6    | 0.680# | Ea   |
| FB7554 | 37020 | 3/4 x 54"  | 1   | 6    | 0.950# | Ea   |
| FB7572 | 37025 | 3/4 x 72"  | 1   | 6    | 1.220# | Ea   |

### Flex-A-Bit Tool

|       |       |     |   |   |        |    |
|-------|-------|-----|---|---|--------|----|
| FG357 | 37040 | All | 1 | 6 | 0.450# | Ea |
|-------|-------|-----|---|---|--------|----|



## Pilot Drills & Accessories PC 6390



- 1/4" High Speed Drill Pilot
- Split Point Design
- Caution! Always Wear Eye Protection

Pilot drills are available with three flats or three notches. Set screws secure drill in arbor.

| CAT NO | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| VPD4   | 28540 | 4-1/2 x 1/4" Pilot Drill, Shank Ground 3 Sides                                    | 1   | 10   | 0.050# | Ea   |
| VPD4N  | 28545 | 4-1/2 x 1/4" Pilot Drill, 3 Notches for Set Screw                                 | 1   | 10   | 0.050# | Ea   |
| VPD4S  | 28550 | 3-1/16" Pilot Drill for V24K, V34, & V35P Arbors                                  | 1   | 10   | 0.050# | Ea   |
| VE121  | 28555 | 12" Extension for 7/16" Arbors  | 1   | 1    | 0.800# | Ea   |
| V44N   | 28560 | Adapter Nut- Adapts Arbor with 1/2-20 threads to fit Hole Saw with 5/8-18 Threads | 1   | 1    | 0.650# | Ea   |

See new products at [lhdottie.com](http://lhdottie.com)

Dottie

E7



## Hole Saws PC 6380

Variable pitch hole saws are bi-metal construction with an M3 HSS cutting edge which is laser welded to a spring steel back. They will cut to depths of 1-3/8" and will outlast carbon steel hole saws, while the tooth design resists shock and strippage. The saws accept standard arbors and will cut stainless steel, iron, pipe, wood and plastic.

- Bi Metal
- M3 Steel RC65-66
- Shatterproof
- 4/6 Variable Pitch
- Powder Coated
- Accepts Standard Arbors
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DIAMETER | USE ARBOR      | PIPE SIZE |        |     |      | WT/STD | UNIT |
|--------|-------|----------|----------------|-----------|--------|-----|------|--------|------|
|        |       |          |                | TAP       | ENTR.  | STD | MSTR |        |      |
| VP09   | 28400 | 9/16"    | V24K, V34, V44 |           |        | 1   | 10   | 0.080# | Ea   |
| VP10   | 28402 | 5/8"     | V24K, V34, V44 |           |        | 1   | 10   | 0.090# | Ea   |
| VP11   | 28404 | 11/16"   | V24K, V34, V44 |           |        | 1   | 10   | 0.090# | Ea   |
| VP12   | 28406 | 3/4"     | V24K, V34, V44 |           | 3/8"   | 1   | 10   | 0.090# | Ea   |
| VP13   | 28408 | 13/16"   | V24K, V34, V44 |           |        | 1   | 10   | 0.110# | Ea   |
| VP14   | 28410 | 7/8"     | V24K, V34, V44 | 3/4"      | 1/2"   | 1   | 10   | 0.110# | Ea   |
| VP15   | 28412 | 15/16"   | V24K, V34, V44 |           |        | 1   | 10   | 0.130# | Ea   |
| VP16   | 28414 | 1"       | V24K, V34, V44 |           |        | 1   | 10   | 0.140# | Ea   |
| VP18   | 28416 | 1-1/8"   | V24K, V34, V44 | 1"        | 3/4"   | 1   | 10   | 0.190# | Ea   |
| VP19   | 28418 | 1-3/16"  | V24K, V34, V44 |           |        | 1   | 10   | 0.200# | Ea   |
| VP20   | 28420 | 1-1/4"   | V35P, V45P     |           |        | 1   | 10   | 0.200# | Ea   |
| VP21   | 28422 | 1-5/16"  | V35P, V45P     |           |        | 1   | 10   | 0.210# | Ea   |
| VP22   | 28424 | 1-3/8"   | V35P, V45P     |           | 1"     | 1   | 10   | 0.240# | Ea   |
| VP24   | 28426 | 1-1/2"   | V35P, V45P     |           |        | 1   | 10   | 0.280# | Ea   |
| VP26   | 28428 | 1-5/8"   | V35P, V45P     |           |        | 1   | 10   | 0.340# | Ea   |
| VP28   | 28430 | 1-3/4"   | V35P, V45P     | 1-1/2"    | 1-1/4" | 1   | 10   | 0.230# | Ea   |
| VP30   | 28432 | 1-7/8"   | V35P, V45P     |           |        | 1   | 10   | 0.270# | Ea   |
| VP32   | 28434 | 2"       | V35P, V45P     |           | 1-1/2" | 1   | 10   | 0.290# | Ea   |
| VP34   | 28436 | 2-1/8"   | V35P, V45P     |           |        | 1   | 10   | 0.330# | Ea   |
| VP36   | 28438 | 2-1/4"   | V35P, V45P     | 2"        |        | 1   | 10   | 0.360# | Ea   |
| VP37   | 28440 | 2-5/16"  | V35P, V45P     |           |        | 1   | 10   | 0.330# | Ea   |
| VP38   | 28442 | 2-3/8"   | V35P, V45P     |           |        | 1   | 10   | 0.330# | Ea   |
| VP40   | 28444 | 2-1/2"   | V45P           |           | 2"     | 1   | 10   | 0.450# | Ea   |
| VP41   | 28446 | 2-9/16"  | V45P           |           |        | 1   | 10   | 0.450# | Ea   |
| VP48   | 28448 | 3"       | V45P           |           | 2-1/2" | 1   | 10   | 0.600# | Ea   |
| VP56   | 28450 | 3-1/2"   | V45P           |           |        | 1   | 10   | 0.620# | Ea   |
| VP58   | 28452 | 3-5/8"   | V45P           |           | 3"     | 1   | 10   | 0.660# | Ea   |
| VP64   | 28454 | 4"       | V45P           |           |        | 1   | 10   | 0.810# | Ea   |
| VP66   | 28456 | 4-1/8"   | V45P           |           | 3-1/2" | 1   | 10   | 0.850# | Ea   |
| VP70   | 28458 | 4-3/8"   | V45P           |           |        | 1   | 10   | 0.910# | Ea   |
| VP72   | 28460 | 4-1/2"   | V45P           |           |        | 1   | 10   | 0.960# | Ea   |
| VP76   | 28462 | 4-3/4"   | V45P           |           | 4"     | 1   | 10   | 1.030# | Ea   |
| VP80   | 28464 | 5"       | V45P           |           |        | 1   | 10   | 1.140# | Ea   |
| VP88   | 28466 | 5-1/2"   | V45P           |           |        | 1   | 10   | 1.300# | Ea   |
| VP96   | 28468 | 6"       | V45P           |           |        | 1   | 10   | 1.530# | Ea   |



## Arbors PC 6390

Arbors are supplied with pilot drills. Check Hole Saw to determine proper arbor.

- Interchangeable With Other Brands
- Includes Replaceable High Speed Pilot Drill
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | SHANK      | THREAD SIZE | DRILL SIZE | DRILL NUMBER | DRILL SIZE | CHUCK FITS     | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------|-------------|------------|--------------|------------|----------------|-----|------|--------|------|
| V24K   | 28500 | 1/4" Round | 1/2-20      | 1/4"       | VPD4         | 1/4"       | 9/16" - 1-1/8" | 1   | 1    | 0.130# | Ea   |
| V34    | 28505 | 3/8" Hex   | 1/2-20      | 1/4"       | VDP4S        | 3/8"       | 9/16" - 1-1/8" | 1   | 1    | 0.150# | Ea   |
| V35P   | 28510 | 3/8" Hex   | 5/8-18      | 1/4"       | VPD4S        | 3/8"       | 1-1/4" - 6"    | 1   | 1    | 0.360# | Ea   |
| V44    | 28515 | 7/16" Hex  | 1/2-20      | 1/4"       | VPD4         | 1/2"       | 9/16" - 1-1/8" | 1   | 1    | 0.160# | Ea   |
| V45P   | 28525 | 7/16" Hex  | 5/8-18      | 1/4"       | VPD4         | 1/2"       | 1-1/4" - 6"    | 1   | 1    | 0.500# | Ea   |



# Hole Saw Kits PC 6400



- Packed In Molded Cases
- Variable Pitch
- Bi-Metal Blades

- Caution! Always Wear Eye Protection

Hole saw kits are supplied with the most popular sizes for the electrician and plumber. The VP100 contains 9 popular electrical and plumbing saws, while the VP02E & VP08 are for the electrical conduit sizes. These kits contain the necessary arbors for all the hole saws.

| CAT NO | UPC | HOLE SAWS | ARBORS | STD | MSTR | WT/STD | UNIT |
|--------|-----|-----------|--------|-----|------|--------|------|
|--------|-----|-----------|--------|-----|------|--------|------|

### Electrician's Hole Saw Kit (Contains 6 Electrical Conduit Sizes 1/2" - 2")

|       |       |   |             |             |   |   |        |    |
|-------|-------|---|-------------|-------------|---|---|--------|----|
| VP02E | 28470 | VP14 7/8"<br>VP18 1-1/8"<br>VP22 1-3/8"<br>VP28 1-3/4"<br>VP32 2" | VP40 2-1/2" | V44<br>V45P | 1 | 1 | 2.700# | Ea |
|-------|-------|---|-------------|-------------|---|---|--------|----|



### Maintenance Hole Saw Kit (Contains 9 Plumbing and Electrical Conduit Sizes 3/8" - 2")

|       |       |  |   |                                     |   |   |        |    |
|-------|-------|--|---|-------------------------------------|---|---|--------|----|
| VP100 | 28472 | VP12 3/4"<br>VP14 7/8"<br>VP18 1-1/8"<br>VP22 1-3/8" | VP24 1-1/2"<br>VP28 1-3/4"<br>VP32 2"<br>VP36 2-1/4"<br>VP40 2-1/2" | V24K V44<br>V45P<br>VE121 Extension | 1 | 1 | 4.820# | Ea |
|-------|-------|--|---|-------------------------------------|---|---|--------|----|



### Master Electrician's Hole Saw Kit (Contains 10 Electrical Conduit Sizes 1/2" - 4")

|      |       |   |   |                                     |   |   |        |    |
|------|-------|---|---|-------------------------------------|---|---|--------|----|
| VP08 | 28474 | VP14 7/8"<br>VP18 1-1/8"<br>VP22 1-3/8"<br>VP28 1-3/4"<br>VP32 2" | VP40 2-1/2"<br>VP48 3"<br>VP58 3-5/8"<br>VP66 4-1/8"<br>VP72 4-1/2" | V24K V44<br>V45P<br>VE121 Extension | 1 | 1 | 7.800# | Ea |
|------|-------|---|---|-------------------------------------|---|---|--------|----|



# Kan-Cut Saws & Kits PC 6440



- Solid One Piece Construction
- Continuous Carbide Grit Edge

- Safer To Use
- New 5" Size
- Caution! Always Wear Eye Protection

Kan Cut saws effectively cut through stucco, lath and plaster or two sheets of 5/8" drywall in one pass to a depth of two inches. Fits most major brands Halo, Capri, Marco, Juno, Prescolite, Progress, Lithonia, Lightolier and others. Arbor not included use V45P.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-----|------|-----|------|--------|------|
|--------|-----|------|-----|------|--------|------|

### Kan-Cut Fixture Saws

|      |       |        |   |   |        |    |
|------|-------|--------|---|---|--------|----|
| 358C | 15960 | 3-5/8" | 1 | 1 | 0.880# | Ea |
| 425C | 15962 | 4-1/4" | 1 | 1 | 1.060# | Ea |
| 438C | 15975 | 4-3/8" | 1 | 1 | 1.080# | Ea |
| 550C | 81781 | 5-1/2" | 1 | 1 | 1.500# | Ea |
| 638C | 15980 | 6-3/8" | 1 | 1 | 1.990# | Ea |
| 658C | 15985 | 6-5/8" | 1 | 1 | 2.050# | Ea |
| 678C | 15990 | 6-7/8" | 1 | 1 | 2.070# | Ea |



|      |       |       |   |   |        |    |
|------|-------|-------|---|---|--------|----|
| V45P | 28525 | Arbor | 1 | 1 | 0.500# | Ea |
|------|-------|-------|---|---|--------|----|

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-----|-------------|-----|------|--------|------|
|--------|-----|-------------|-----|------|--------|------|

### Kan-Cut Hole Saw Kits

|       |       |  |   |   |        |    |
|-------|-------|--|---|---|--------|----|
| KC100 | 17175 | One Ea: 638C Kan Cut, V45P Arbor & KC case       | 1 | 1 | 3.830# | Ea |
| KC200 | 17180 | One Ea: 425C, 638C Kan Cut, V45P Arbor & KC case | 1 | 1 | 4.280# | Ea |



**Caution:** Always wear eye protection. Penetrate the material at 90°. Hole saws may have a tendency to grab, causing injury. **Do Not Exceed 800 RPM.**

## ReciproBlades PC 6450

Bi-metal blades have a flexible spring steel back and are laser welded to a hardened edge. Each blade is designed for a specific use and condition. "Tuff-Grit" carbide blades will cut cast iron.

- Bi Metal 8% Cobalt
- Vacuum Heat Treated
- Tooth Hardness RC66-68
- Powder Coated
- Made in USA
- 5 Per Pouch, Priced Per Blade
- Caution! Wear Eye Protection

| CAT NO   | UPC   | LENGTH | WIDTH | THICKNESS | TPI | APPLICATION  | STD | MSTR | WT/STD | UNIT |
|--|-------|--------|-------|-----------|-----|--|-----|------|--------|------|
| R414B  | 31300 | 4"     | 5/8"  | 0.035     | 14  | Heavy gauge metal, 1/8" thick and above.             | 5   | 5    | 0.130# | Ea   |
| R418B  | 31305 | 4"     | 5/8"  | 0.035     | 18  | Heavy gauge metal, 18 gauge to 1/8" thick.           | 5   | 5    | 0.110# | Ea   |
| R424B  | 31310 | 4"     | 5/8"  | 0.035     | 24  | Metal cutting, 18 gauge and under.                   | 5   | 5    | 0.130# | Ea   |
| R610B7   | 31315 | 6"     | 3/4"  | 0.035     | 10  | Nail-embedded wood, non-ferrous metal.               | 5   | 5    | 0.200# | Ea   |
| R614B7   | 31320 | 6"     | 3/4"  | 0.035     | 14  | Heavy gauge metal, 1/8" thick and above.             | 5   | 5    | 0.210# | Ea   |
| R618B7   | 31325 | 6"     | 3/4"  | 0.035     | 18  | Heavy gauge metal, 18 gauge to 1/8" thick.           | 5   | 5    | 0.210# | Ea   |
| R624B7   | 31330 | 6"     | 3/4"  | 0.035     | 24  | Metal cutting, 18 gauge and under.                   | 5   | 5    | 0.210# | Ea   |
| R810B7   | 31335 | 8"     | 3/4"  | 0.035     | 10  | Nail-embedded wood, plastic, non-ferrous metal.      | 5   | 5    | 0.280# | Ea   |
| R814B7   | 31340 | 8"     | 3/4"  | 0.035     | 14  | General rough-in, metal cutting, nail-embedded wood. | 5   | 5    | 0.280# | Ea   |
| R656BR   | 31345 | 6"     | 3/4"  | 0.050     | 6   | Wood contours, nail-embedded wood.                   | 5   | 5    | 0.210# | Ea   |
| R656BS   | 31350 | 6"     | 3/4"  | 0.050     | 6   | General rough-in, all woods nail-embedded wood.      | 5   | 5    | 0.220# | Ea   |
| R956BR   | 31355 | 9"     | 3/4"  | 0.050     | 6   | General rough-in, all woods nail-embedded wood.      | 5   | 5    | 0.370# | Ea   |
| R156BR   | 31360 | 12"    | 3/4"  | 0.050     | 6   | General rough-in, all woods nail-embedded wood.      | 5   | 5    | 0.530# | Ea   |
| <b>Carbide "Tuf-Grit" Edge (One per pouch)</b> |       |        |       |           |     |  |     |      |        |      |
| R800TG   | 31365 | 8"     | 3/4"  | 0.040     | n/a | Cast iron pipe.                                      | 1   | 1    | 0.090# | Ea   |



## Utility Saw PC 6559

The utility saw with its straight wooden handle is easier to manipulate than a pistol grip saw when cutting openings in drywall.

- 6" Blade
- Individual Display Pack
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION | LENGTH | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|--------|-----|------|--------|------|
| UT6    | 28960 | Utility Saw | 6"     | 1   | 24   | 0.180# | Ea   |

## Hacksaw Frame PC 6470



- Use as Jab or Compass Saw
- 45° & 90° Miter Angle
- High Leverage Tension Arm
- Blade Storage in Handle
- Industrial Quality Die Cast
- Made In USA

This versatile hacksaw has a heavy duty cast aluminum handle and steel crossbar. Lightweight and well balanced for greater control.

| CAT NO | UPC   | DESCRIPTION                      | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------------------------|-----|------|--------|------|
| F4     | 28975 | Industrial Quality Hacksaw Frame | 1   | 6    | 1.470# | Ea   |

## Hacksaw Blades PC 6580



- Bi Metal
- Boxed Or Pouch
- Industrial Quality
- Caution! Always Wear Eye Protection

Bi-metal hacksaw blades cut tough and hard material fast and outlasts standard carbon blades by a factor of three to one. Bi-metal blades offer a super sharp high speed steel cutting edge, laser welded to a flexible alloy back. Bi-metal blades offer straight cuts and long life in high tension frames and allow the greatest possible user safety.

| CAT NO  | UPC   | LENGTH | TPI | STD | MSTR | WT/STD | UNIT |
|---------|-------|--------|-----|-----|------|--------|------|
| HSB18T* | 29350 | 12"    | 18  | 10  | 100  | 0.430# | Ea   |
| HSB18TB | 29340 | 12"    | 18  | 100 | 100  | 4.300# | Ea   |
| HSB24T* | 29355 | 12"    | 24  | 10  | 100  | 0.430# | Ea   |
| HSB24TB | 29343 | 12"    | 24  | 100 | 100  | 4.300# | Ea   |
| HSB32T* | 29360 | 12"    | 32  | 10  | 100  | 0.430# | Ea   |
| HSB32TB | 29345 | 12"    | 32  | 100 | 100  | 4.300# | Ea   |

\* Pouch

## PVC Saw & Replacement Blades PC 6560



- Tooth Design Cuts On Both Strokes
- Filed Teeth
- 12" Handle With Blade
- 18" Handle With Blade
- Caution! Always Wear Eye Protection

The PVC Bi-Saw is designed for PVC and cuts on both the front and back stroke. The offset handle allows cutting at ground level while permitting hand clearance. The die cast, offset handle is interchangeable with most popular brands of replacement blades.

| CAT NO  | UPC   | DESCRIPTION                | STD | MSTR | WT/STD | UNIT |
|---------|-------|----------------------------|-----|------|--------|------|
| PVC12BH | 29380 | 12" Handle & Blade         | 1   | 5    | 0.660# | Ea   |
| PVC18BH | 29382 | 18" Handle & Blade         | 1   | 5    | 0.770# | Ea   |
| 12BLD   | 29384 | 12" Replacement Blade Only | 1   | 5    | 0.330# | Ea   |
| 18BLD   | 29386 | 18" Replacement Blade Only | 1   | 5    | 0.460# | Ea   |

## Snaggletooth Pro Saw PC 6559



- Easily Cuts Wallboard, Drywall, Plywood, & Plastic
- Blade Cuts In Both Directions
- Laser Cut Triple Ground Teeth
- Triangular Handle

The Snaggletooth Pro Saw is the right tool for cutting openings for electrical outlets, and the hardened tip penetrates drywall easily eliminating the need to drill.

| CAT NO | UPC   | DESCRIPTION          | LENGTH                | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------------|-----------------------|-----|------|--------|------|
| SNG6   | 42092 | Snaggletooth Pro Saw | 6" Blade/ 12" Overall | 1   | 12   | 0.350# | Ea   |



## Safety Helmets & Ratchet Safety Helmets PC 6616

Safety helmets are required on most job sites. The woven nylon suspension is comfortable and absorbs impact. On the ratchet model the head size can be adjusted without removing the helmet, providing a no slip hold – even in the most physically active job.

- |   |   |   |
|---|---|---|
| <ul style="list-style-type: none"> <li>• Lightweight High Density Polyethylene</li> <li>• Short Peak and Trim Profile</li> <li>• Rain Trough Side &amp; Back</li> <li>• Universal Accessory Slot</li> <li>• Removable Cushioned Brow Pad</li> </ul> | <ul style="list-style-type: none"> <li>• 4-Point Impact Absorbing Suspension</li> <li>• Quick Slide Sizing From 6-1/2 to 7-3/4"</li> <li>• USA Made Meets ANSI Z89 1-1997 Type I class C, E &amp; G Requirements</li> </ul> | <b>Ratchet Helmet:</b> <ul style="list-style-type: none"> <li>• 6-Point Impact Absorbing Suspension</li> <li>• Ratchet EZ Turn Knob</li> <li>• Sizes 6-1/2" to 8", 40 Increments</li> </ul> |
|---|---|---|

| CAT NO                        | UPC   | COLOR  | STD | MSTR | WT/STD | UNIT |
|-------------------------------|-------|--------|-----|------|--------|------|
| SFTY                          | 11635 | Yellow | 1   | 6    | 0.750# | Ea   |
| SFTW                          | 11636 | White  | 1   | 6    | 0.750# | Ea   |
| SFTO                          | 11637 | Orange | 1   | 6    | 0.750# | Ea   |
| <b>Ratchet Safety Helmets</b> |       |        |     |      |        |      |
| SFTYR                         | 11638 | Yellow | 1   | 6    | 0.890# | Ea   |
| SFTWR                         | 11639 | White  | 1   | 6    | 0.890# | Ea   |



## Rain Suit PC 6618

The heavy duty yellow rain suit consists of three pieces; extra large cut jacket, detachable hood, and bib overalls.

- 100% Waterproof & Non-Conductive
- High Visibility Safety Yellow
- Heavy Duty 35mm PVC Bonded To Polyester

### Jacket

- Detachable Hood & Corduroy Collar
- Large Reinforced Flapped Pockets
- Adjustable Wrist & Waist For Snug Fit
- Ventilated Underarm & Back For Better Circulation

### Bib Overalls

- Snap Fly Front
- Adjustable Suspenders
- Ankle & Waist Adjustment For Better Fit

| CAT NO   | UPC   | DESCRIPTION              | SIZE     | STD | MSTR | WT/STD | UNIT |
|----------|-------|--------------------------|----------|-----|------|--------|------|
| R6900M   | 31381 | 3-PC Heavy Duty Rainsuit | Medium   | 1   | 6    | 3.330# | Ea   |
| R6900L   | 31382 | 3-PC Heavy Duty Rainsuit | Large    | 1   | 6    | 3.400# | Ea   |
| R6900XL  | 31383 | 3-PC Heavy Duty Rainsuit | X-Large  | 1   | 6    | 3.480# | Ea   |
| R69002XL | 31384 | 3-PC Heavy Duty Rainsuit | 2X-Large | 1   | 6    | 3.560# | Ea   |



## Safety Vests PC 6617

Safety vests are now OSHA compliant - meeting or exceeding the new standards for reflectivity (ANSI/ISEA 107-1999 Class II Garments).

- Hi Viz Lime With Silver Reflective Tape
- 100% Polyester Knit
- 2" Reflective Trim
- Zipper Closure

| CAT NO | UPC   | SIZE    | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------|-----|------|--------|------|
| SVM    | 11640 | Medium  | 1   | 6    | 0.530# | Ea   |
| SVL    | 11641 | Large   | 1   | 6    | 0.540# | Ea   |
| SVXL   | 11642 | X-Large | 1   | 6    | 0.560# | Ea   |



## Dust Mask PC 5310

CAUTION: Do Not Use As Protection From; Asbestos, Silica or Cotton Dust, Toxic Dust, Fumes, Mists, Gas or Vapor. NOT TO BE USED IN SPRAY PAINT OPERATIONS!

- General Purpose

| CAT NO | UPC   | DESCRIPTION                        | STD      | MSTR     | WT/STD | UNIT  |
|--------|-------|------------------------------------|----------|----------|--------|-------|
| MSK50  | 30450 | General Purpose Dust Mask          | 50       | 500      | 1.140# | C     |
| MSK55  | 30455 | General Purpose Dust Mask (5 pack) | 12 packs | 24 packs | 0.580# | Ea Pk |



- Kit Exceeds Federal OSHA Requirements
- Serves up to 25 People
- Molded Handle For Carry Or Mount Kit On Work Site

No office, vehicle, or worksite should be without this compact emergency First Aid Kit. The FK25E comes in a polypropylene case and includes all the supplies you need for up to 25 people.

**FK25E**

**Small 25 Person Contractor Kit**

- 1 Plastic First Aid Case
- 1 Cold Pack Unit Sz. 5" x 6" Box
- 1 Swift 1x3 Plastic 50/Box
- 1 First Aid Pack for 25 Kit
- 1 ABD Combine Pad 5" x 9"
- 1 Adhesive Tape W/P 1" x 5 Yd.
- 1 Gauze Clean-Wrap Bdge. N/S 2"
- 1 Tri-Bndg. Non Woven 40" x 40" x 56"
- 1 Eye Wash Single Use 1/2 Oz.
- 1 Burn Gel 1/8 Oz. Pks 6 Ea.
- 1 Scissor 4-1/2" Blue Handle
- 1 Tweezer 3" Square End
- 1 Swift Woven Assorted 20/Box
- 1 First Aid Booklet
- 1 2 Pr. Vinyl Gloves Zip Lock Bag

| CAT NO | UPC   | DESCRIPTION                 | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------|-----|------|--------|------|
| FK25E  | 10270 | 25 Person Contractor Kit    | 1   | 10   | 1.50#  | Ea   |
| FKR25E | 10271 | 25 Person Contractor Refill | 1   | 10   | 0.94#  | Ea   |

- Meets Kit Requirement For ANSI Z308.1
- Serves Up To 50 People
- Molded Handle For Carry or Mount Kit On Work Site

An emergency can happen at any time – anywhere your work force goes to do their job. This well stocked emergency first aid kit supplies all your office, factory or work site needs for up to 50 people. Packed in a polypropylene case.



**FK50E**

**Medium 50 Person Contractor Kit**

- 1 Plastic First Aid Case
- 1 Tri-Bndg. Non Woven 40" x 40" x 56"
- 2 Cold Pack Unit Sz. 5" x 6" Box
- 1 Scissor 4-1/2" Blue Handle
- 1 Tweezer 3" Square End
- 1 Non-Adherent Pads 2" x 3" 10'S
- 4 Ammonia Inhalants Ampule Ea.
- 1 PVP Iodine Wipes 10/Un.
- 1 Swift 1" x 3" Plastic 100/Box
- 2 Gauze Clean-Wrap Bdge. N/S 2"
- 2 Gauze Clean-Wrap Bdge. N/S 1"
- 1 Gauze Clean-Wrap Bdge. N/S 3"
- 1 Eye Wash Single Use 1/2 Oz.
- 1 Triple-Biotic Oint. .5 Gram 10
- 1 Gze. Pads Sterile 3" x 3" 10'S
- 1 Gze. Pads Sterile 2" x 2" 10'S
- 1 Burn Gel 1/8 Oz. Pks. 6 Ea.
- 2 ABD Combine Pad 5" x 9"
- 1 First Aid Booklet
- 1 Wound Cleaner
- 1 Adhesive Tape W/P 1" x 5 Yd.
- 1 Eye Pads /Adhs. Strips 4 Ea.
- 1 2 Pr. Vinyl Gloves Zip Lock Bag

| CAT NO | UPC   | DESCRIPTION                 | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------|-----|------|--------|------|
| FK50E  | 81819 | 50 Person Contractor Kit    | 1   | 10   | 2.25#  | Ea   |
| FKR50E | 81820 | 50 Person Contractor Refill | 1   | 10   | 1.50#  | Ea   |

- Meets Kit Requirement For ANSI Z308.1
- Serves Up To 75 People
- Molded Handle For Carry or Mount Kit On Work Site

Stock your large facility or work site with this complete emergency first aid kit. This durable kit is packed with a large assortment of first aid supplies to meet your needs. Packed in a polypropylene case.



**FK75E**

**Large 75 Person Contractor Kit**

- 1 Plastic First Aid Case
- 1 Tri-Bndg. Non Woven 40" x 40" x 56"
- 2 Cold Pack Unit Sz. 5" x 6" Box
- 1 Scissor 4-1/2" Blue Handle
- 1 Tweezer 3" Square End
- 1 Non-Adherent Pads 2" x 3" 10'S
- 4 Ammonia Inhalants Ampule Ea.
- 1 PVP Iodine Wipes 10/Un.
- 1 Swift 1" x 3" Plastic 100/Box
- 2 Gauze Clean-Wrap Bdge. N/S 2"
- 2 Gauze Clean-Wrap Bdge. N/S 1"
- 2 Gauze Clean-Wrap Bdge. N/S 3"
- 2 Eye Wash Single Use 1/2 Oz.
- 2 Triple-Biotic Oint. .5 Gram 10.
- 1 Gze. Pads Sterile 3" x 3" 10'S
- 1 Gze. Pads Sterile 2" x 2" 10'S
- 1 Burn Gel 1/8 Oz. Pks. 6 Ea.
- 2 ABD Combine Pad 5" x 9"
- 1 Wound Cleaner
- 1 Adhesive Tape W/P 1" x 5 Yd.
- 1 Eye Pads W/Adhs. Strips 4 Ea.
- 2 2 Pr. Vinyl Gloves Zip Lock Bag
- 1 Swift Woven Assorted 20/Bx
- 1 First Aid Booklet

| CAT NO | UPC   | DESCRIPTION                 | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------|-----|------|--------|------|
| FK75E  | 81821 | 75 Person Contractor Kit    | 1   | 10   | 2.25#  | Ea   |
| FKR75E | 81822 | 75 Person Contractor Refill | 1   | 10   | 1.50#  | Ea   |



**Kodiak**



**Razor**



**Komodo**



**Protective Eyewear  
PC 6610**

- Exceeds ANSI Z87.1 & CSA Z94.3 Safety Standards
- 100% UV & UVB Protection Against Harmful Radiation
- Ultra Light, Durable & Precise Fit Frames
- Impact Resistant Polycarbonate Lens
- Distortion Free 2.2 mm Lens For Optimum Clarity
- Exceptional Peripheral Vision Protection
- Variety of Coated Lens Tints
- Hangable Display Pack

Industrial safety eyewear is designed to protect you. Available in a variety of styles, finishes and lens color tints, they are designed down to the smallest detail to provide optimal performance with state of the art comfort, style and protection.

| CAT NO  | UPC   | STYLE  | FRAME              | LENS              | STD | MSTR | WT/STD | UNIT |
|---------|-------|--------|--------------------|-------------------|-----|------|--------|------|
| EKOD110 | 10923 | Kodiak | Matte Black        | Gray              | 1   | 10   | 0.11#  | Ea   |
| EKOD175 | 10924 | Kodiak | Matte Black        | Dark Blue Mirror  | 1   | 10   | 0.11#  | Ea   |
| EKOD440 | 10925 | Kodiak | Crystal Blue       | Gray Mirror       | 1   | 10   | 0.11#  | Ea   |
| EKOD685 | 10926 | Kodiak | Shiny Silver       | Dark Blue Mirror  | 1   | 10   | 0.11#  | Ea   |
| EKOD740 | 10927 | Kodiak | Crystal Red        | Gray Mirror       | 1   | 10   | 0.11#  | Ea   |
| ERAZ100 | 11984 | Razor  | Matte Black        | Clear             | 1   | 10   | 0.11#  | Ea   |
| ERAZ110 | 11985 | Razor  | Matte Black        | Gray              | 1   | 10   | 0.11#  | Ea   |
| ERAZ120 | 11986 | Razor  | Matte Black        | Yellow            | 1   | 10   | 0.11#  | Ea   |
| ERAZ160 | 11987 | Razor  | Matte Black        | Dark Brown Mirror | 1   | 10   | 0.11#  | Ea   |
| ERAZ175 | 11988 | Razor  | Matte Black        | Dark Blue Mirror  | 1   | 10   | 0.11#  | Ea   |
| EKMD000 | 81814 | Komodo | Crystal Clear      | Clear             | 1   | 10   | 0.11#  | Ea   |
| EKMD110 | 81815 | Komodo | Crystal Black      | Clear             | 1   | 10   | 0.11#  | Ea   |
| EKMD550 | 81816 | Komodo | Amber              | Brown             | 1   | 10   | 0.11#  | Ea   |
| EKMD840 | 81817 | Komodo | Gun Metal Gray     | Gray Mirror       | 1   | 10   | 0.11#  | Ea   |
| EKMD870 | 81818 | Komodo | Gun Metal Lt. Blue | Blue Mirror       | 1   | 10   | 0.11#  | Ea   |



**Softframe Goggles  
PC 6610**

Soft, clear vinyl Goggle with universal bridge provides all day comfort and exceptional protection against dust and flying debris. Around-the-lens ventilation minimizes lens fogging. Comfortable over prescription glasses or when worn alone.

- Clear Anti-Fog Lens
- Cap Vented Clear Softframe

| CAT NO | UPC   | DESCRIPTION      | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------|-----|------|--------|------|
| 206F   | 40150 | Softframe Goggle | 1   | 10   | 0.26#  | Ea   |



**Ear Protection  
PC 6615**

One pair per polybag. Packed 200 pair per dispenser box.

- ANSI S3.19-1974
- Noise Reduction Rate NRR 30db
- Low Pressure Foam Plugs
- Self Adjusting
- Non Allergenic
- Non Irritating

| CAT NO | UPC   | DESCRIPTION       | STD    | MSTR   | WT/STD | UNIT    |
|--------|-------|-------------------|--------|--------|--------|---------|
| MLE200 | 11645 | MaxLite Ear Plugs | 200 Pr | 200 Pr | 0.94#  | Ea Pair |

**Shoe Covers  
PC 6771**



- Anti-Static
- Impervious Material
- Non-linting
- EZ On-EZ Off

| CAT NO | UPC   | DESCRIPTION           | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------|-----|------|--------|------|
| SC     | 59880 | 50 Shoe Covers in Jar | 1   | 10   | 0.90#  | Ea   |



## Cable Saw PC 6535

- Quick Release Contour Handles
- Constructed with Stainless Cable
- Caution! Always Wear Eye Protection

The Cable Saw easily cuts through PVC conduit. The quick release handle allows the cable saw blade to easily cut around PVC in hard to reach areas.



| CAT NO | UPC   | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|-----|------|--------|------|
| CS100  | 28967 | Cable Saw   | 1   | 10   | 0.22#  | Ea   |

## Reel Spinner PC 6522

- Disassembles For Easy Transportation

Reel Spinner is a wire dispenser which can be made to accommodate a variable number of spools of wire by utilizing available EMT (tubing). The leg & axle assembly use 1/2" EMT which is cut to length as required. The leg & axle assembly are easily assembled and secured by hand tightening the wing nuts. The length of EMT cut for the axle will determine the amount of spools it will accommodate.



| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------------|-----|------|--------|------|
| RS896  | 17237 | Reel Spinner | 1   | 10   | 0.49#  | Ea   |

## Power Wire Nut Driver PC 6700

- Tested And Proven To Cut Labor By 66% By Electrical Contractors
- Caution! Always Wear Eye Protection

This multipurpose tool will handle most brands of wire connectors. Used in a power drill or screwdriver it saves wear and tear on wrists and fingers. Made of high impact plastic with a 1/4" metal shank.



| CAT NO | UPC   | DESCRIPTION                  | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------------------|-----|------|--------|------|
| CX1    | 24100 | Power Driver with 1/4" Shank | 1   | 10   | 0.07#  | Ea   |

## Tape Measure PC 6525

- Heat Treated Mylar Coated Blade
- Durable ABS Case w/ Rubber Grip
- Extends 25 ft.
- Self Supporting Over 8 ft.
- Triple Riveted
- Positive Double Lock
- Excellent Return Function
- Packed 24 Per Display Box or Individual Cards
- Caution! Always Wear Eye Protection



| CAT NO                 | UPC   | COLOR                 | SIZE     | STD | MSTR | WT/STD | UNIT    |
|------------------------|-------|-----------------------|----------|-----|------|--------|---------|
| <b>Counter Display</b> |       |                       |          |     |      |        |         |
| TMO                    | 11620 | Orange                | 1" x 25' | 24  | 24   | 18.96# | Ea Tape |
| TMG                    | 11621 | Green                 | 1" x 25' | 24  | 24   | 18.96# | Ea Tape |
| TMY                    | 11622 | Yellow                | 1" x 25' | 24  | 24   | 18.96# | Ea Tape |
| TMC                    | 11623 | Chrome                | 1" x 25' | 24  | 24   | 18.96# | Ea Tape |
| TMA                    | 11624 | Assorted (6 Ea Color) | 1" x 25' | 24  | 24   | 18.96# | Ea Tape |
| <b>Display Card</b>    |       |                       |          |     |      |        |         |
| TMOH                   | 11627 | Orange                | 1" x 25' | 1   | 12   | 0.854# | Ea Tape |
| TMGH                   | 11626 | Green                 | 1" x 25' | 1   | 12   | 0.854# | Ea Tape |
| TMYH                   | 11628 | Yellow                | 1" x 25' | 1   | 12   | 0.854# | Ea Tape |
| TMCH                   | 11625 | Chrome                | 1" x 25' | 1   | 12   | 0.854# | Ea Tape |



### Lock Back Knife PC 6510

- Lightweight ABS Handle w/ Clip
- Quick Change Blade Mechanism
- One Hand Opening Mechanism
- Spring Blade Release
- Includes Blade Storage & 6 Blades
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| LBK    | 10880 | Folding Lock-Back Utility Knife Replacement Blades0          | 1   | 12   | 0.550# | Ea   |
| UBK    | 16502 | Double Pointed Replacement Blades One Card Contains 5 Blades | 1   | 12   | 0.050# | Ea   |



### Professional Knife & Tool Sharpener PC 6524

The knife sharpener anyone can use! No messy oils or stones. Sharpens knives in less that 10 seconds! It even works on serrated knives. Perfect tool for Electricians, Plumbers and Heating and Air Installers.

- Large Ergonomic Handle
- Full Length Finger Guard
- Diamond Honed Tungsten Carbide Sharpening Blades
- Sharpener Will Not Rust
- Easily Cleaned With Soap And Water
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION                         | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------------------------|-----|------|--------|------|
| KS1    | 14660 | Professional Knife & Tool Sharpener | 1   | 12   | 0.30#  | Ea   |



### K-PVC Cutter PC 6540

The KPVC cutter is an economical cutter for schedule 40 PVC, and its heavy blade makes easy work of it. Affordability and quality in one package.

- Heavy Duty Blade
- Cuts 1/2", 3/4" & 1" Schedule 40 PVC
- Blades Are Replaceable
- Caution! Always Wear Eye Protection

| CAT NO                               | UPC   | DESCRIPTION        | STD | MSTR | WT/STD | UNIT |
|--------------------------------------|-------|--------------------|-----|------|--------|------|
| KPVC                                 | 28980 | K-PVC Cutter       | 1   | 6    | 0.830# | Ea   |
| <b>PVC Cutter Replacement Blades</b> |       |                    |     |      |        |      |
| KB                                   | 28985 | Replacement Blades | 1   | 6    | 0.160# | Ea   |



### Wire Stripper / Cutter PC 6590

This handy Wire Stripper/Cutter has been one of the most popular wire strippers contractors use. It is effective and fits easily in a pouch or pocket.

- Adjustable
- Cushion Grip
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION                      | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------------------------|-----|------|--------|------|
| DS1    | 28995 | Adjustable Stripper Cushion Grip | 1   | 10   | 0.140# | Ea   |



### Quick Leader PC 6595

The Dottie Quick Leader is designed for maximum flexibility, curving around bends in conduit with ease. It is for a 1/8 inch wide steel fish tape and will pull up to 500lbs.

- For 1/8 Inch Wide Steel Fish Tapes
- Flexible Leader Makes Quick Work of Tight Bends
- Pulls Up To 500 Lbs.
- Guides Steel Fish Tape Around Bends In Conduit
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | SIZE | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|--------------|-----|------|--------|------|
| QL12   | 11967 | 12"  | Quick Leader | 1   | 10   | 0.124# | Ea   |

# Quick Sticks PC 6055



- Quick Sticks Will Flex Up To 90° Without Breaking
- Made From High Strength, Low Weight Fiberglass Material
- Made in USA
- Available Attachments: Pulling Hooks, Pulling Eyes, And Whisk
- Lite Sticks "Glow" In The Dark For Better Visibility During Use
- Caution! Always Wear Eye Protection

Dottie Quick Sticks offer unmatched durability to reach over drop ceilings, through insulated walls, as well as under floors and in any confined space. They are flexible enough to bend to the angle you need, yet rigid enough to push through insulation.

| CAT NO     | UPC   | SIZE        | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|------------|-------|-------------|---|-----|------|--------|------|
| QS3630     | 23132 | 3/16" x 30' | Tube Contains: Five - 3/16" x 6' Red Rods & Two Pulling Eyes            | 1   | 1    | 2.000# | Ea   |
| QS3630LS   | 23134 | 3/16" x 30' | Tube Contains: Five - 3/16" x 6' Lite Stick Rods & Two Pulling Eyes     | 1   | 1    | 2.000# | Ea   |
| QS3612     | 23136 | 3/16" x 12' | Kit Contains: Four - 3/16" x 3' Red Rods w/ Pulling Eye & Hook          | 1   | 1    | 1.000# | Ea   |
| QS3612LS   | 23140 | 3/16" x 12' | Kit Contains: Four - 3/16" x 3' Lite Stick Rods w/ Pulling Eye & Hook   | 1   | 1    | 1.000# | Ea   |
| QS3612X4   | 23166 | 3/16" x 12' | Tube Contains: Three - 3/16" x 4' Red Rods w/ Pulling Eye & Hook        | 1   | 1    | 1.000# | Ea   |
| QS3612X4LS | 23165 | 3/16" x 12' | Tube Contains: Three - 3/16" x 4' Lite Stick Rods w/ Pulling Eye & Hook | 1   | 1    | 1.000# | Ea   |
| QS2524     | 23130 | 1/4" x 24'  | Tube Contains: Four - 1/4" x 6' White Rods & Two Pulling Eyes           | 1   | 1    | 2.000# | Ea   |
| QS2524LS   | 23158 | 1/4" x 24'  | Tube Contains: Four - 1/4" x 6' Lite Stick Rods & Two Pulling Eyes      | 1   | 1    | 2.000# | Ea   |
| QS2512     | 23138 | 1/4" x 12'  | Kit Contains: Four - 1/4" x 3' White Rods w/ Pulling Eye & Hook         | 1   | 1    | 1.000# | Ea   |
| QS2512X4   | 23156 | 1/4" x 12'  | Kit Contains: Three - 1/4" x 4' White Rods w/ Pulling Eye & Hook        | 1   | 1    | 1.000# | Ea   |
| QS2512LS   | 23155 | 1/4" x 12'  | Kit Contains: Three - 1/4" x 4' Lite Stick Rods w/ Pulling Eye & Hook   | 1   | 1    | 1.000# | Ea   |

### Quick Sticks Accessories

|        |       |       |                               |   |   |        |    |
|--------|-------|-------|-------------------------------|---|---|--------|----|
| QSPE36 | 23146 | 3/16" | 3/16" Replacement Pulling Eye | 1 | 1 | 0.010# | Ea |
| QSPH36 | 23148 | 3/16" | 3/16" Pulling Hook            | 1 | 1 | 0.010# | Ea |
| QSW36  | 23152 | 3/16" | 3/16" Whisk (egg beater) Head | 1 | 1 | 0.010# | Ea |
| QSPE25 | 23142 | 1/4"  | 1/4" Replacement Pulling Eye  | 1 | 1 | 0.010# | Ea |
| QSPH25 | 23144 | 1/4"  | 1/4" Pulling Hook             | 1 | 1 | 0.010# | Ea |
| QSW25  | 23150 | 1/4"  | 1/4" Whisk (egg beater) Head  | 1 | 1 | 0.010# | Ea |



Whisk  
QSW36  
QSW25



Hooks  
QSPH36  
QSPH25



Eyes  
QSPE36  
QSPE25

## TECH TALK



### Dottie Quick Sticks

Quick Sticks screw together to reach full or desired length. Use to fish wires through walls, under floors, over suspended ceilings and into many other confined spaces. Quick Sticks will flex up to 90° without breaking. Made from high strength, low weight fiber glass material. Quick Sticks are ideal for pulling and stringing communication wires, alarm system wires, romex, telephone and thermostat wire. Available attachments are; Pulling Hooks, Pulling Eyes and Whisk Heads. Our glow in the dark version is available in 3/16" & 1/4" diameter.





## Extension Cords PC 6800

Dottie's new line of contractor grade extension cords in both 14/3 SJTW and 12/3 SJTW are UL listed and meet the professional contractor's requirements for outdoor use. They are all-purpose, portable cords that remain flexible even under extreme weather conditions (Temp. Range rated -40 degrees to 140 degrees). Our quality construction provides excellent resistance to abrasion, oil, grease and chemicals. All cords include lighted female ends showing the cord has been powered up for safety.

- Available In 13 Or 15 Amp.
- Wattage Rated At 1625 Or 1875
- Conductor Blade / Pin Designed To Prevent Break-Off Or Pull-Out
- Light Embedded In The Female Connector Lights To Let You Know The Power Is On.
- Triple Tap Provided On 100 Ft. Cords Allowing Additional Outlets For Power Distribution.
- Cord Remians Flexible Even Under The Most Extreme Weather Conditions



| CAT NO    | UPC   | SIZE    | COLOR  | AWG  | WIRE TYPE | AMPS | WATTS | STD | MSTR | WT/STD  | UNIT |
|-----------|-------|---------|--|------|-----------|------|-------|-----|------|---------|------|
| PEC14350  | 81769 | 50 Ft.  | Green Cord/Yellow Stripe-with clear lighted end            | 14/3 | SJTW      | 15   | 1875  | 12  | 12   | 56.30#  | Ea   |
| PEC143100 | 81770 | 100 Ft. | Green Cord/Yellow Stripe-with clear lighted-Triple Tap end | 14/3 | SJTW      | 13   | 1625  | 6   | 6    | 58.40 # | Ea   |
| PEC12350  | 81771 | 50 Ft.  | Yellow Cord/Green Stripe-with clear lighted end            | 12/3 | SJTW      | 15   | 1875  | 8   | 8    | 56.00#  | Ea   |
| PEC123100 | 81772 | 100 Ft. | Yellow Cord/Green Stripe-with clear lighted-Triple Tap end | 12/3 | SJTW      | 15   | 1625  | 6   | 6    | 58.40 # | Ea   |



## Adapters PC 6805

Dottie's new line of Contractor Grade Adapters are UL listed and meet the professional contractors requirements for outdoor use. They are designed to provide the ultimate flexibility when arranging portable power needs at the job site.

- 12/3 STW
- Available In 15 Or 20 Amp.
- Wattage Rated At 1875 Or 2500
- Solid Molded Vinyl Connectors

| CAT NO   | UPC   | SIZE  | COLOR  | AWG  | WIRE TYPE | AMPS | WATTS | STD | MSTR | WT/STD | UNIT |
|----------|-------|-------|--|------|-----------|------|-------|-----|------|--------|------|
| PAY12315 | 81773 | 2 Ft. | Yellow Cord Y Adaptor Straight (15 Amp)          | 12/3 | STW       | 15   | 2500  | 1   | 12   | 1.46#  | Ea   |
| PAY12320 | 81775 | 2 Ft. | Yellow Cord Y Adaptor Straight (20 Amp)          | 12/3 | STW       | 20   | 2500  | 1   | 12   | 1.46#  | Ea   |
| PAW12315 | 81774 | 2 Ft. | Yellow Cord W Adaptor Straight (15 Amp)          | 12/3 | STW       | 15   | 2500  | 1   | 12   | 1.88#  | Ea   |
| PAW12320 | 81776 | 2 Ft. | Yellow Cord W Adaptor Straight (20 Amp)          | 12/3 | STW       | 20   | 2500  | 1   | 12   | 1.88#  | Ea   |
| PAS12315 | 81894 | 2 Ft. | Yellow Cord Straight Adaptor (15 Amp)            | 12/3 | STW       | 15   | 1875  | 1   | 12   | 0.55#  | Ea   |
| PAS12320 | 81895 | 2 Ft. | Yellow Cord Straight Adaptor (20 Amp)            | 12/3 | STW       | 20   | 1875  | 1   | 12   | 0.55#  | Ea   |
| PAT12315 | 81896 | 2 Ft. | Yellow Cord Straight Triple Tap Adaptor (15 Amp) | 12/3 | STW       | 15   | 1875  | 1   | 12   | 1.04#  | Ea   |



PAY



PAW



PAS



PAT






The Ultimate-X Power batteries are manufactured to deliver high-performance results and are quality guaranteed to equal or exceed any standard alkaline battery in the market. Manufactured under ISO-90001-2004 and ISO-14003-2000 Certificates to guarantee manufacturing excellence, the Ultimate X-Power dry cell batteries deliver superior results without the added overhead costs of nationally advertised brands.


| CAT NO              | UPC   | DESCRIPTION              | STD | MSTR | WT/STD | UNIT    |
|---------------------|-------|--------------------------|-----|------|--------|---------|
| <b>Carded Packs</b> |       |                          |     |      |        |         |
| BATAACARD           | 00018 | 1 Card - 4 AAA Batteries | 12  | 48   | 1.55#  | Ea Card |
| BATAACARD           | 00016 | 1 Card - 4 AA Batteries  | 12  | 48   | 2.90#  | Ea Card |
| BATCCARD            | 00020 | 1 Card - 2 C Batteries   | 12  | 48   | 4.15#  | Ea Card |
| BATDCARD            | 00021 | 1 Card - 2 D Batteries   | 12  | 48   | 9.75#  | Ea Card |
| BAT9VCARD           | 00022 | 1 Card - 1 9V Battery    | 12  | 48   | 1.70#  | Ea Card |



|                         |       |                           |    |    |        |         |
|-------------------------|-------|---------------------------|----|----|--------|---------|
| <b>Contractor Packs</b> |       |                           |    |    |        |         |
| BATAAA                  | 00030 | 1 Pack - 24 AAA Batteries | 12 | 24 | 9.70#  | Ea Pack |
| BATAA                   | 00029 | 1 Pack - 24 AA Batteries  | 12 | 24 | 16.10# | Ea Pack |
| BATC                    | 00031 | 1 Pack - 12 C Batteries   | 12 | 12 | 23.00# | Ea Pack |
| BATD                    | 00032 | 1 Pack - 12 D Batteries   | 12 | 12 | 46.20# | Ea Pack |
| BAT9V                   | 00033 | 1 Pack - 8 9V Batteries   | 12 | 12 | 11.76# | Ea Pack |



# TECH TALK





## 13 in 1 Ratcheting Screwdriver PC 6755



The new 13 in 1 cushion gripped ratcheting screwdriver is the latest edition to our popular line up of multi bit drivers. With its smooth patent pending ZAD 8 zinc alloy precision 28 tooth ratcheting mechanism, it delivers over 225 lbs of torque strength, which makes driving fasteners faster and easier than ever before. The convenient storage handle is loaded with six double-ended bits for a total of twelve different standard sized drivers. The 1/4" Hex drive shaft is great for driving 1/4" hex head screws. This is definitely a top of the line tool every professional contractor should have in his or her tool bag.



- Convenient Storage For A Wide Range Of Bits
- 1/4" Hex Driver Shaft - Great For 1/4" Hex Head Screws
- Patent Pending ZAD 8 Zinc Alloy SOLID-CORE™ Ratchet Delivers Over 225 lbs Of Torque Strength
- Display Pack
- Precision 28 Tooth Ratchet Makes Driving Fasteners Faster And Easier. Limited Lifetime Warranty.
- Heavy Duty Nylon Reinforced Handle & Chamfered Solid Steel Shaft For Long Life & Durability
- Cushion Grip, Tapered Designed Handle - Extra Comfort And Less Fatigue



Patented Pullout Bit Cartridge



Phillips  
0+3 1+2



Square  
1+2



Star  
T10+T15 T20+T25



Slotted  
4+6



Hex  
1/4"

| CAT NO | UPC   | CAP/BODY  | DESCRIPTION                    | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|--------------------------------|-----|------|--------|------|
| D131R  | 81251 | Red/Black | 13 in 1 Ratcheting Screwdriver | 1   | 10   | 0.50#  | Ea   |



## Nickel Plated Replacement Bits For Multi Bit Drivers- PC 6768

- Packed Two Per Card
- For Multi Bit Drivers
- Resists Corrosion

| CAT NO   | UPC   | DESCRIPTION                  | STD | MSTR | WT/STD | UNIT |
|----------|-------|------------------------------|-----|------|--------|------|
| NBT1015C | 81951 | T10 & T15 Star               | 1   | 5    | 0.020# | Ea   |
| NBT2025C | 81952 | T20 & T25 Star               | 1   | 5    | 0.020# | Ea   |
| NBP03C   | 81953 | 0 & 3 Phillips               | 1   | 5    | 0.020# | Ea   |
| NBP12C   | 81954 | 1 & 2 Phillips               | 1   | 5    | 0.020# | Ea   |
| NBS03C   | 81955 | 0 & 3 Square Recess          | 1   | 5    | 0.020# | Ea   |
| NBS12C   | 81956 | 1 & 2 Square Recess          | 1   | 5    | 0.020# | Ea   |
| NBSL46C  | 81957 | 4 & 6 Slotted                | 1   | 5    | 0.020# | Ea   |
| RBVC     | 81958 | Valve Stem Bit + 5.5 Slotted | 1   | 5    | 0.020# | Ea   |
| SA14C*   | 81959 | 1/4" Socket Adaptor          | 1   | 5    | 0.020# | Ea   |

\* Unplated



## Tamper Proof Replacement Bits For Multi Bit Drivers - PC 6769

- Packed Two Per Card
- For Multi Bit Drivers
- Resists Corrosion

| CAT NO  | UPC   | DESCRIPTION         | STD | MSTR | WT/STD | UNIT |
|---------|-------|---------------------|-----|------|--------|------|
| RTP15C  | 81960 | T10 & T15 Star Pin  | 1   | 5    | 0.020# | Ea   |
| RTP20C  | 81961 | T20 & T25 Star Pin  | 1   | 5    | 0.020# | Ea   |
| RTP27C  | 81962 | T27 & T30 Star Pin  | 1   | 5    | 0.020# | Ea   |
| RHP18C  | 81963 | 1/8 & 9/64 Hex Pin  | 1   | 5    | 0.020# | Ea   |
| RHP532C | 81964 | 5/32 & 3/16 Hex Pin | 1   | 5    | 0.020# | Ea   |
| RSP68C  | 81965 | 6 & 8 Spanner       | 1   | 5    | 0.020# | Ea   |
| RSP12C  | 81966 | 10 & 12 Spanner     | 1   | 5    | 0.020# | Ea   |

## 15 in 1 Screwdriver PC 6762



- Palm Saving Rotation Cap
- Rotating Balance Point Collar
- Retracting Bit Storage
- High Impact Triax Housing
- Spring Loaded Ball Bearing Bit
- Full Length Solid Steel Shaft
- 59+ Rockwell Hardness
- Made In USA
- Display Pack

The Original Standard 15 in 1 driver contains seven double ended bits for a total of fourteen different standard drivers. The 1/4" shank fits any 1/4" hex power grooved bits and is also great for driving 1/4" hex head screws.




| CAT NO | UPC   | CAP/BODY     | DESCRIPTION         | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------------|---------------------|-----|------|--------|------|
| D151   | 10282 | Yellow/Green | 15 in 1 Screwdriver | 1   | 10   | 0.490# | Ea   |

## Tamper Proof 15 in 1 Screwdriver PC 6763



- Contains Common Security Bit Load
- Specially Loaded For (note cut off)

This 15 in 1 Tamper Proof driver is a must for all commercial/industrial tradesmen (Electricians, Security, etc.). The 15 in 1 Tamper Proof comes loaded with the most common security bits, including: Spanner, Hex pin and Star pin.



| CAT NO | UPC   | CAP/BODY  | DESCRIPTION                      | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|----------------------------------|-----|------|--------|------|
| D151TP | 10266 | Red/Black | 15 in 1 Tamper Proof Screwdriver | 1   | 10   | 0.550# | Ea   |

## Stainless Steel 15 in 1 Screwdriver PC 6762



- Expressly Made For Outdoors And Marine Environments
- 14 Different Bit Sizes
- Standarded Bitload

15 in 1 Stainless screwdriver is loaded with electroless nickel plated bits for use in areas where high corrosion or humidity are an issue. The driver is equipped with a stainless steel shaft.



| CAT NO | UPC   | CAP/BODY    | DESCRIPTION                         | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|-------------------------------------|-----|------|--------|------|
| D151SS | 10265 | Yellow/Blue | 15 in 1 Stainless Steel Screwdriver | 1   | 10   | 0.512# | Ea   |

## HVAC 14 in 1 Screwdriver PC 6761



- Specially Loaded For The Heating, Ventilation And Air Conditioning Industry

14 in 1 HVAC multi bit screwdriver is loaded with the most common HVAC bits, including a valve stem bit.



| CAT NO   | UPC   | CAP/BODY  | DESCRIPTION              | STD | MSTR | WT/STD | UNIT |
|----------|-------|-----------|--------------------------|-----|------|--------|------|
| D151HVAC | 10267 | Red/Black | 14 in 1 HVAC Screwdriver | 1   | 10   | 0.512# | Ea   |



### 8 in 1 Stubby Ratchet Driver PC 6772



Includes the following bits:

- #1, #2 x 2pcs
- #1, #2 x 2pcs
- 1/4", 3/16"

- Contractor Preferred/Industrial Grade
- Includes 8 Industrial Quality Bits
- Non-Slip Grip Design
- High Torque 3 Way Reversible Ratchet Mechanism
- Easy Bit Storage in Handle

| CAT NO | UPC   | DESCRIPTION                  | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------------------|-----|------|--------|------|
| SRD8   | 43089 | 8 in 1 Stubby Ratchet Driver | 1   | 12   | 0.374# | Ea   |



### 8 in 1 Stubby Ratchet Driver (Tamper Proof) PC 6778



Includes the following bits:

- T15, T20, T25
- 1/8", 5/32"
- #6, #8, #10

- Contractor Preferred/Industrial Grade
- Includes 8 Industrial Quality Bits
- Non-Slip Grip Design
- High Torque 3 Way Reversible Ratchet Mechanism
- Easy Bit Storage in Handle

| CAT NO | UPC   | DESCRIPTION                               | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| SRD8TP | 36090 | 8 in 1 Tamper Proof Stubby Ratchet Driver | 1   | 12   | 0.374# | Ea   |



### Pocket Pakratchet PC 6671



Dottie's Pakratchet puts seven common sockets into a small yet strong tool that no tool bag should be without.

- Light Weight, Durable High Torque Composite
- Corrosion Resistant
- High Quality Chrome Vanadium Steel 6 Point Socket
- Push Button Socket Release
- Ergonomic, Non-Conductive Handle

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| PR7    | 81943 | 7 pc. Pocket Pakratchet 1/4" SAE Drive. Socket Sizes Included 1/4", 9/32", 5/16", 11/32" 3/8", 7/16", 1/2" | 1   | 10   | 0.50#  | Ea   |



### Tamper Proof Hand Drivers PC 6670

- Full Size Driver
- Steel Blade Oversized
- Acetate Handle

| CAT NO          | UPC   | SCREW SIZE   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|-----------------|-------|--------------|--------------|-----|------|--------|------|
| <b>One Way</b>  |       |              |              |     |      |        |      |
| OW68            | 23000 |              | Removal Tool | 1   | 10   | 0.250# | Ea   |
| OW810           | 23005 | #6-#8        | Removal Tool | 1   | 10   | 0.310# | Ea   |
| OW1214          | 23010 | #12-#14      | Removal Tool | 1   | 10   | 0.350# | Ea   |
| <b>Spanner</b>  |       |              |              |     |      |        |      |
| SPN6            | 23015 | #6           | Spanner      | 1   | 10   | 0.220# | Ea   |
| SPN8            | 23020 | #8           | Spanner      | 1   | 10   | 0.220# | Ea   |
| SPN10           | 23025 | #10          | Spanner      | 1   | 10   | 0.220# | Ea   |
| <b>Star Pin</b> |       |              |              |     |      |        |      |
| STR10           | 23030 | #6BH         | Star Pin     | 1   | 10   | 0.180# | Ea   |
| STR15           | 23035 | #6FH-#8BH    | Star Pin     | 1   | 10   | 0.180# | Ea   |
| STR20           | 23040 | #8FH         | Star Pin     | 1   | 10   | 0.180# | Ea   |
| STR25           | 23045 | #10FH, #10BH | Star Pin     | 1   | 10   | 0.190# | Ea   |
| STR27           | 23050 | 1/4FH-1/4BH  | Star Pin     | 1   | 10   | 0.210# | Ea   |
| STR30           | 23052 | 1/4FH        | Star Pin     | 1   | 10   | 0.220# | Ea   |

## Compact Combo Bit Kit PC 6340

- 31 Piece Assorted Standard and Tamper Proof
- Packed In A Belt Mount Case
- Contains Most Popular Sizes of Standard and Tamper Proof Bits



### 31 Piece Assortment Kit contains the following:

- Square Drive 1 Ea IB0, IB1, IB2, IB3
- Phillips 1 Ea IB0P, IB1P, (IB2P 2 Ea), IB3P
- Slotted 1 Ea IB0S, IB1S, (IB2S 2 Ea), IB3S
- Star Pin 1 Ea 60TR10, 15, 20, 25, 27, 30,
- Spanner 1 Ea 115-6, 115-8, 115-10, 115-12, 115-14
- Hex Pin 1 Ea 73TR3, 5, 7, 8, 9
- Bit Holder 1 Ea QCA14

This 31 piece bit kit contains the most often used Standard and Tamper Proof bits in a compact storage case, which is sized to fit in a contractor's pouch or can be easily attached to a belt. Includes a quick change bit holder.

| CAT NO | UPC   | DESCRIPTION                                  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| IB31PK | 23190 | 31 Assorted Bits w/ Quick Release Bit Holder | 1   | 6    | 0.500# | Ea   |

## Standard Bit Kit PC 6760

### 31 Piece Assortment Kit contains the following:

- Slotted 1 Ea IB0S, IB1S, IB2S, IB3S, IB5S
- Phillips 1 Ea IB1P, IB2P, IB3P
- Hex Socket 1 Ea IB564, IB332, IB764, IB18, IB964 & IB532
- Square 1 Ea IB0, IB1, IB2, IB3
- Star 1 Ea IB10, IB15, IB20, IB25, IB30, IB40
- Pozidrive 1 Ea IBPZ1, IBPZ2
- Clutch 1 Ea IBC2, IBC3
- Magnetic Bit Holder 1 Ea MBH
- Magnetic Hand Driver 1 Ea MHD
- Socket Adapter 1 Ea SHA14114
- Storage Case 1 Ea SCR

The Standard Bit Driver Kit contains the full compliment of the most popular bits. The kit is provided with a magnetic hand driver, a socket adapter, and a magnetic bit holder for use in power tools.

- 31 Piece Assortment
- Packed In Sturdy Polypro Case

| CAT NO | UPC   | DESCRIPTION             | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------------|-----|------|--------|------|
| LS1    | 60250 | 31 pc. Standard Bit Kit | 1   | 1    | 1.130# | Ea   |

## Tamper Proof Bit Kit PC 6760

### 31 Piece Assortment Kit contains the following:

- Slotted 1 Ea IB1S, IB2S, IB3S
- Phillips 1 Ea IB1P, IB2P, IB3P
- Square 1 Ea IB1, IB2, IB3
- Spanner 1 Ea 115-6, 115-8, 115-10
- Star Pin 1 Ea 60TR7, 8, 9, 10, 15, 20, 25, 27, 30, 40
- Hex Socket 1 Ea 73TR3, 4, 5, 6, 7, 8
- Magnetic Bit Holder 1 Ea MBH
- Magnetic Hand Driver 1 Ea MHD
- Socket Adapter 1 Ea SHA14114
- Storage Case 1 Ea SCR

The Tamper Proof Bit Driver Kit contains the full compliment of the most popular bits. The kit is provided with a magnetic hand driver, a socket adapter, and a magnetic bit holder for use in power tools.

- 31 Piece Assortment
- Packed In Sturdy Polypro Case

| CAT NO | UPC   | DESCRIPTION                 | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------------------|-----|------|--------|------|
| LS1TP  | 60253 | 31 pc. Tamper Proof Bit Kit | 1   | 1    | 1.130# | Ea   |

## Magnetic Hand Driver PC 6720



- High Impact Storage Handle
- Fits 1/4" Insert Bits
- Magnetic

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| MHD    | 16949 | Magnetic Hand Driver<br>8" with Storage Compartments | 1   | 1    | 0.22#  | Ea   |

# Bits & Tools PC 6650



Insert and power bits are available in a variety of configurations. Bits of 1" length are insert bits; bits 2" and longer are power bits. Note: MBH Tool is used with insert bits only. Not to be used with power bits.

- Maximum Durability
- Precision Fit Prevents Wear

TOOLS & SPECIALTY ITEMS > BITS & TOOLS

| CAT NO                             | UPC   | TYPE  | SCREW SIZE | POINT SIZE / LENGTH | STD | MSTR | WT/STD | UNIT |
|------------------------------------|-------|---|------------|---------------------|-----|------|--------|------|
| <b>Phillips Pt. Size 0 &amp; 1</b> |       |   |            |                     |     |      |        |      |
| IB0P                               | 60205 | Insert Bit  | #4         | #0 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1P                               | 60222 | Insert Bit  | #6         | #1 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1PL                              | 60224 |  Power Bit   | #6         | #1 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB1PX                              | 60346 |  Power Bit   | #6         | #1 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB1P4                              | 60348 | Power Bit   | #6         | #1 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB1P6                              | 60360 | Power Bit   | #6         | #1 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Phillips Pt. Size 2</b>         |       |   |            |                     |     |      |        |      |
| IB2P                               | 60226 | Insert Bit  | #8-10      | #2 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB2PL                              | 60228 |  Power Bit   | #8-10      | #2 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB2PX                              | 60230 |  Power Bit   | #8-10      | #2 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB2P4                              | 60362 | Power Bit   | #8-10      | #2 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB2P6                              | 60364 | Power Bit   | #8-10      | #2 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Phillips Pt. Size 3</b>         |       |   |            |                     |     |      |        |      |
| IB3P                               | 60232 | Insert Bit  | #12-14     | #3 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB3PL                              | 60234 | Power Bit   | #12-14     | #3 x 2"             | 5   | 50   | 0.230# | Ea   |
| IB3PX                              | 60366 |  Power Bit   | #12-14     | #3 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB3P4                              | 60368 | Power Bit   | #12-14     | #3 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB3P6                              | 60370 | Power Bit   | #12-14     | #3 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Slotted Pt. Size 0 &amp; 1</b>  |       |   |            |                     |     |      |        |      |
| IB0S                               | 60202 | Insert Bit  | #4         | #0 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1S                               | 60210 | Insert Bit  | #6         | #1 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1SL                              | 60372 |  Power Bit   | #6         | #1 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB1SX                              | 60374 |  Power Bit  | #6         | #1 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB1S4                              | 60376 | Power Bit   | #6         | #1 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB1S6                              | 60378 | Power Bit   | #6         | #1 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Slotted Pt. Size 2</b>          |       |   |            |                     |     |      |        |      |
| IB2S                               | 60212 | Insert Bit  | #8-10      | #2 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB2SL                              | 60214 |  Power Bit | #8-10      | #2 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB2SX                              | 60216 |  Power Bit | #8-10      | #2 x 3"             | 5   | 100  | 0.170# | Ea   |
| IB2S4                              | 60380 | Power Bit   | #8-10      | #2 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB2S6                              | 60382 | Power Bit   | #8-10      | #2 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Slotted Pt. Size 3</b>          |       |   |            |                     |     |      |        |      |
| IB3S                               | 60218 | Insert Bit  | #12-14     | #3 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB3SL                              | 60384 |  Power Bit | #12-14     | #3 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB3SX                              | 60386 |  Power Bit | #12-14     | #3 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB3S4                              | 60388 | Power Bit   | #12-14     | #3 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB3S6                              | 60390 | Power Bit   | #12-14     | #3 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Square Pt. 0 &amp; 1</b>        |       |   |            |                     |     |      |        |      |
| IB0                                | 60320 | Insert Bit  | #4         | #0 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1                                | 60200 | Insert Bit  | #6         | #1 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB1L                               | 60322 |  Power Bit | #6         | #1 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB1X                               | 60324 |  Power Bit | #6         | #1 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB14                               | 60326 | Power Bit   | #6         | #1 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB16                               | 60328 | Power Bit   | #6         | #1 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Square Pt. Size 2</b>           |       |   |            |                     |     |      |        |      |
| IB2                                | 16940 | Insert Bit  | #8-10      | #2 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB2L                               | 60204 | Power Bit   | #8-10      | #2 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB2X                               | 60330 |  Power Bit | #8-10      | #2 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB24                               | 60332 | Power Bit   | #8-10      | #2 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB26                               | 60334 | Power Bit   | #8-10      | #2 x 6"             | 5   | 50   | 0.360# | Ea   |
| <b>Square Pt. Size 3</b>           |       |   |            |                     |     |      |        |      |
| IB3                                | 16943 | Insert Bit  | #12-14     | #3 x 1"             | 10  | 100  | 0.100# | Ea   |
| IB3L                               | 60336 | Power Bit   | #12-14     | #3 x 2"             | 10  | 100  | 0.230# | Ea   |
| IB3X                               | 60338 |  Power Bit | #12-14     | #3 x 3"             | 5   | 50   | 0.170# | Ea   |
| IB34                               | 60340 | Power Bit   | #12-14     | #3 x 4"             | 5   | 50   | 0.236# | Ea   |
| IB36                               | 60342 | Power Bit   | #12-14     | #3 x 6"             | 5   | 50   | 0.360# | Ea   |

# Magnetic Hex Tools PC 6700, 6710, 6720

- Hardened Core For Extra Strength
- Heat Treated To Resist Wear
- Specially Designed To Reduce Stripping



\*Magnetic Bit Holder      Socket Adapter Extension  
\* MBH: to be used for Insert Bits Only. Not for power bits.




| CAT NO   | UPC   | TYPE                | SCREW SIZE     | DRIVE LENGTH   | STD | MSTR | WT/STD | UNIT |
|--|-------|---------------------|----------------|----------------|-----|------|--------|------|
| <b>Magnetic Hex Tools</b>                        |       |                     |                |                |     |      |        |      |
| MT8  | 17730 |                     | #6-8           | 1/4 x 1-3/4"   | 1   | 10   | 0.070# | Ea   |
| MT8L   | 17735 |                     | #6-8           | 1/4 x 2-9/16"  | 1   | 10   | 0.080# | Ea   |
| MT84   | 17737 | 1/4"                | #6-8           | 1/4 x 4"       | 1   | 10   | 0.110# | Ea   |
| MT86   | 17739 |                     | #6-8           | 1/4 x 6"       | 1   | 10   | 0.190# | Ea   |
| <hr/>  |       |                     |                |                |     |      |        |      |
| MT10   | 17740 |                     | #10-12         | 5/16 x 1-3/4"  | 1   | 10   | 0.070# | Ea   |
| MT10L  | 17745 |                     | #10-12         | 5/16 x 2-9/16" | 1   | 10   | 0.090# | Ea   |
| MT104  | 17742 | 5/16"               | #10-12         | 5/16 x 4"      | 1   | 10   | 0.110# | Ea   |
| MT106  | 17747 |                     | #10-12         | 5/16 x 6"      | 1   | 10   | 0.190# | Ea   |
| <hr/>  |       |                     |                |                |     |      |        |      |
| MT38   | 17760 |                     | 1/4"           | 3/8 x 1-3/4"   | 1   | 10   | 0.080# | Ea   |
| MT38L  | 17752 |                     | 1/4"           | 3/8 x 2-9/16"  | 1   | 10   | 0.090# | Ea   |
| MT384  | 17757 | 3/8"                | 1/4"           | 3/8 x 4"       | 1   | 10   | 0.130# | Ea   |
| MT386  | 17759 |                     | 1/4"           | 3/8 x 6"       | 1   | 10   | 0.190# | Ea   |
| <hr/>  |       |                     |                |                |     |      |        |      |
| <b>Magnetic Bit Holder &amp; Drive - PC 6710</b> |       |                     |                |                |     |      |        |      |
| MBH*   | 16948 | Magnetic Bit Holder |                | 1/4 x 3"       | 1   | 10   | 0.110# | Ea   |
| <hr/>  |       |                     |                |                |     |      |        |      |
| <b>Socket Adapter Extensions - PC 6720</b>       |       |                     |                |                |     |      |        |      |
| SHA14114   | 23105 |                     | 1/4" Hex Shank | 1/4 x 1-1/4"   | 1   | 10   | 0.032# | Ea   |
| SHA142   | 23108 | 1/4"                | 1/4" Hex Shank | 1/4 x 2"       | 1   | 10   | 0.034# | Ea   |
| SHA143   | 23111 |                     | 1/4" Hex Shank | 1/4 x 3"       | 1   | 10   | 0.050# | Ea   |
| <hr/>  |       |                     |                |                |     |      |        |      |
| SHA382   | 23114 |                     | 1/4" Hex Shank | 3/8 x 2"       | 1   | 10   | 0.044# | Ea   |
| SHA383   | 23117 | 3/8"                | 1/4" Hex Shank | 3/8 x 3"       | 1   | 10   | 0.082# | Ea   |
| SHA384   | 23120 |                     | 1/4" Hex Shank | 3/8 x 4"       | 1   | 10   | 0.109# | Ea   |

## Tamper Proof Insert Bits PC 6720

| CAT NO          | UPC   | SCREW SIZE  | DESCRIPTION   | LENGTH | STD | MSTR | WT/STD | UNIT |
|-----------------|-------|-------------|---------------|--------|-----|------|--------|------|
| <b>Hex Pin</b>  |       |             |               |        |     |      |        |      |
| 73TR3           | 22733 | #4-5        | 3/32" Hex Pin | 1"     | 1   | 5    | 0.010# | Ea   |
| 73TR5           | 22735 | #6          | 1/8" Hex Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 73TR7           | 22737 | #8,10,12,14 | 5/32" Hex Pin | 1"     | 1   | 5    | 0.010# | Ea   |
| 73TR8           | 22738 | 5/16        | 3/16" Hex Pin | 1"     | 1   | 5    | 0.010# | Ea   |
| 73TR9           | 22739 | 3/8         | 7/32" Hex Pin | 1"     | 1   | 5    | 0.010# | Ea   |
| <hr/>           |       |             |               |        |     |      |        |      |
| <b>Star Pin</b> |       |             |               |        |     |      |        |      |
| 60TR10          | 22610 | #6R         | T10 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 60TR15          | 22615 | #6F-8R      | T15 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 60TR20          | 22620 | #8F         | T20 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 60TR25          | 22625 | 10F-10R     | T25 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 60TR27          | 22627 | 1/4F 1/4R   | T27 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| 60TR30          | 22630 | 1/4F        | T30 Star Pin  | 1"     | 1   | 5    | 0.010# | Ea   |
| <hr/>           |       |             |               |        |     |      |        |      |
| <b>Spanner</b>  |       |             |               |        |     |      |        |      |
| 1156            | 31156 | #6          | #6 Spanner    | 1"     | 1   | 5    | 0.010# | Ea   |
| 1158            | 31158 | #8          | #8 Spanner    | 1"     | 1   | 5    | 0.010# | Ea   |
| 11510           | 31150 | #10         | #10 Spanner   | 1"     | 1   | 5    | 0.010# | Ea   |
| 11512           | 31152 | #12         | #12 Spanner   | 1"     | 1   | 5    | 0.010# | Ea   |
| 11514           | 31154 | #14         | #14 Spanner   | 1"     | 1   | 5    | 0.010# | Ea   |

### Power and Insert Bit Merchandiser (PBD)

Our attractive counter top Power and Insert Bit Merchandiser has been one of the most popular selling tools in our distributor's showrooms for many years. When fully stocked, our display offers a wide assortment of the most popular power and insert bits to satisfy the needs of every contractor. The clear acrylic lockable lid allows for easy viewing of the product without the concern of shrinkage.





# Carded Bits PC 6751

Insert and power bits are available in a variety of configurations. Bits of 1" length are insert bits; bits 2" and longer are power bits. Note: MBH Tool is used with insert bits only. Not to be used with power bits.

- Packed 2 Per Display Card
- Maximum Durability
- Precision Fit Prevents Wear

| CAT NO  | UPC   | TYPE | SCREW SIZE | POINT SIZE / LENGTH | STD     | MSTR | WT/STD | UNIT  |         |
|---|-------|------|------------|---------------------|---------|------|--------|-------|---------|
| <b>Phillips Pt. Size 0 &amp; 1</b>            |       |      |            |                     |         |      |        |       |         |
| IB0PC   | 81836 |      | Insert Bit | #4                  | #0 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1PC   | 81837 |      | Insert Bit | #6                  | #1 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1PLC  | 81838 |      | Power Bit  | #6                  | #1 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB1PXC  | 81839 |      | Power Bit  | #6                  | #1 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB1P4C  | 81840 |      | Power Bit  | #6                  | #1 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB1P6C  | 81841 |      | Power Bit  | #6                  | #1 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Phillips Pt. Size 2</b>                    |       |      |            |                     |         |      |        |       |         |
| IB2PC   | 81842 |      | Insert Bit | #8-10               | #2 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB2PLC  | 81843 |      | Power Bit  | #8-10               | #2 x 2" | 10   | 100    | 0.02# | Ea Card |
| IB2PXC  | 81844 |      | Power Bit  | #8-10               | #2 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB2P4C  | 81845 |      | Power Bit  | #8-10               | #2 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB2P6C  | 81846 |      | Power Bit  | #8-10               | #2 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Phillips Pt. Size 3</b>                    |       |      |            |                     |         |      |        |       |         |
| IB3PC   | 81847 |      | Insert Bit | #12-14              | #3 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB3PLC  | 81848 |      | Power Bit  | #12-14              | #3 x 2" | 5    | 50     | 0.09# | Ea Card |
| IB3PXC  | 81849 |      | Power Bit  | #12-14              | #3 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB3P4C  | 81850 |      | Power Bit  | #12-14              | #3 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB3P6C  | 81851 |      | Power Bit  | #12-14              | #3 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Slotted Pt. Size 0 &amp; 1</b>             |       |      |            |                     |         |      |        |       |         |
| IB0SC   | 81852 |      | Insert Bit | #4                  | #0 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1SC   | 81853 |      | Insert Bit | #6                  | #1 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1SLC  | 81854 |      | Power Bit  | #6                  | #1 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB1SXC  | 81855 |      | Power Bit  | #6                  | #1 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB1S4C  | 81856 |      | Power Bit  | #6                  | #1 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB1S6C  | 81857 |      | Power Bit  | #6                  | #1 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Slotted Pt. Size 2</b>                     |       |      |            |                     |         |      |        |       |         |
| IB2SC   | 81858 |      | Insert Bit | #8-10               | #2 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB2SLC  | 81859 |      | Power Bit  | #8-10               | #2 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB2SXC  | 81860 |      | Power Bit  | #8-10               | #2 x 3" | 5    | 100    | 0.07# | Ea Card |
| IB2S4C  | 81861 |      | Power Bit  | #8-10               | #2 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB2S6C  | 81862 |      | Power Bit  | #8-10               | #2 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Slotted Pt. Size 3</b>                     |       |      |            |                     |         |      |        |       |         |
| IB3SC   | 81863 |      | Insert Bit | #12-14              | #3 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB3SLC  | 81864 |      | Power Bit  | #12-14              | #3 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB3SXC  | 81865 |      | Power Bit  | #12-14              | #3 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB3S4C  | 81866 |      | Power Bit  | #12-14              | #3 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB3S6C  | 81867 |      | Power Bit  | #12-14              | #3 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Square Pt. 0 &amp; 1</b>                   |       |      |            |                     |         |      |        |       |         |
| IB0C  | 81868 |      | Insert Bit | #4                  | #0 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1C  | 81869 |      | Insert Bit | #6                  | #1 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB1LC   | 81870 |      | Power Bit  | #6                  | #1 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB1XC   | 81871 |      | Power Bit  | #6                  | #1 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB14C   | 81872 |      | Power Bit  | #6                  | #1 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB16C   | 81873 |      | Power Bit  | #6                  | #1 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Square Pt. Size 2</b>                      |       |      |            |                     |         |      |        |       |         |
| IB2C  | 81874 |      | Insert Bit | #8-10               | #2 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB2LC   | 81875 |      | Power Bit  | #8-10               | #2 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB2XC   | 81876 |      | Power Bit  | #8-10               | #2 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB24C   | 81877 |      | Power Bit  | #8-10               | #2 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB26C   | 81878 |      | Power Bit  | #8-10               | #2 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Square Pt. Size 3</b>                      |       |      |            |                     |         |      |        |       |         |
| IB3C  | 81879 |      | Insert Bit | #12-14              | #3 x 1" | 10   | 100    | 0.02# | Ea Card |
| IB3LC   | 81880 |      | Power Bit  | #12-14              | #3 x 2" | 10   | 100    | 0.05# | Ea Card |
| IB3XC   | 81881 |      | Power Bit  | #12-14              | #3 x 3" | 5    | 50     | 0.07# | Ea Card |
| IB34C   | 81882 |      | Power Bit  | #12-14              | #3 x 4" | 5    | 50     | 0.09# | Ea Card |
| IB36C   | 81883 |      | Power Bit  | #12-14              | #3 x 6" | 5    | 50     | 0.14# | Ea Card |
| <b>Combo Pt. Size #2 Square / #2 Phillips</b> |       |      |            |                     |         |      |        |       |         |
| IB2CLC  | 81891 |      | Power Bit  | #8-10               | #2 x 2" | 10   | 100    | 0.02# | Ea Card |



# Carded Bits & Tools PC 6701



- Packed 1 Per Card
- Hardened Core For Extra Strength And Reduced Breakage
- Heat Treated To Resist Breakage And Wear
- Specially Designed To Reduce Stripping

| CAT NO                    | UPC   | TYPE         | SCREW SIZE | POINT SIZE/ LENGTH | STD | MSTR | WT/STD | UNIT |
|---------------------------|-------|--------------|------------|--------------------|-----|------|--------|------|
| <b>Magnetic Hex Tools</b> |       |              |            |                    |     |      |        |      |
| MT8C                      | 81884 |              | #6-8       | 1/4 x 1-3/4"       | 1   | 10   | 0.07#  | Ea   |
| MT8LC                     | 81885 | <b>1/4"</b>  | #6-8       | 1/4 x 2-9/16"      | 1   | 10   | 0.08#  | Ea   |
| MT10C                     | 81886 |              | #10-12     | 5/16 x 1-3/4"      | 1   | 10   | 0.07#  | Ea   |
| MT10LC                    | 81887 | <b>5/16"</b> | #10-12     | 5/16 x 2-9/16"     | 1   | 10   | 0.09#  | Ea   |
| MT38C                     | 81888 |              | 1/4"       | 3/8 x 1-3/4"       | 1   | 10   | 0.08#  | Ea   |
| MT38LC                    | 81889 | <b>3/8"</b>  | 1/4"       | 3/8 x 2-9/16"      | 1   | 10   | 0.09#  | Ea   |



## Magnetic Bit Holder PC 6711

|      |       |                     |          |   |    |       |    |
|------|-------|---------------------|----------|---|----|-------|----|
| MBHC | 81890 | Magnetic Bit Holder | 1/4 x 3" | 1 | 10 | 0.11# | Ea |
|------|-------|---------------------|----------|---|----|-------|----|

Note: To be used with insert bits only. Not power bits.



## Multi Drive Screw Guide Kit PC 6712



The Multi Drive Screw Guide Kit contains the most popular screw driving bits for all your fastening jobs. Drive the most difficult lengths of screws with ease using this professionally designed tool.

| CAT NO | UPC   | CONTAINS  | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| MDSG   | 81912 | 1-Ea Multi Drive Screw Guide<br>1-Ea Phillips #1, #2, #3<br>1-Ea Square #1, #2<br>1-Ea Slotted #6F-#8R, #8R-10F, #10R-12R | 1   | 10   | 0.50#  | Ea   |



# TECH TALK



### Fastener Tools

Dottie provides professional quality Insert & Power Bits, Magnetic Hex Tools and Accessories for all your fastener driving applications including Tamper Proof. Dottie tools and accessories are manufactured using shock resistant tool steel, a proprietary heat treatment process and are precision machined, ensuring maximum durability and an excellent fit which reduces cam out and excessive wear.



Insert & Power Bits



Bit Holders & Extensions



Magnetic Hex Tools



Bit Assortments

See new products at [lhdottie.com](http://lhdottie.com)

Dottie



TOOLS & SPECIALTY ITEMS > CARDED BITS & TOOLS > MAGNETIC BIT HOLDER > MULTI-DRIVE

## Professional Grade Shovels - Fiberglass PC 6780




- 48" Handle Tensioned Fiberglass
- Minimum Breaking Strength of 261 lbs Per DTH6950-1
- Safe From Electrical Shock
- Does Not Absorb Moisture
- Resists Industrial Chemicals
- Ergonomically Designed Grip
- Standard Or D Handle
- Caution! Always Wear Eye Protection

The shovel and grip ends are larger to provide leverage and control while the center tapers to help your hand slide when "slinging" the material away from the hole.

| CAT NO | UPC   | DESCRIPTION      | HANDLE LENGTH  | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------------|----------------|-----|------|--------|------|
| SHR    | 24000 | #2 Round Point   | 48" Handle     | 1   | 5    | 5.05#  | Ea   |
| SHS    | 24005 | #2 Square Point  | 48" Handle     | 1   | 5    | 5.44#  | Ea   |
| SHD    | 24010 | 14" Drain Spade  | 48" Handle     | 1   | 5    | 4.84#  | Ea   |
| SHDSS  | 24025 | 14" Sharpshooter | 27" 'D' Handle | 1   | 5    | 3.77#  | Ea   |
| SHTR4  | 24015 | 4" Trenching     | 48" Handle     | 1   | 5    | 4.31#  | Ea   |
| SHTR5  | 24020 | 5" Trenching     | 48" Handle     | 1   | 5    | 5.20#  | Ea   |
| SPH    | 24040 | Post Hole Digger | 48" Handle     | 1   | 5    | 11.94# | Ea   |

## Sledges & Picks PC 6780



- Super Grip Fiberglass Handle
- Safe From Electrical Shock
- Does Not Absorb Moisture
- Resists Industrial Chemicals
- Caution! Always Wear Eye Protection

Composite construction consists of millions of continuous parallel fiberglass strands cured under tension in a thermosetting resin covered by an engineering plastic cladding for strength, safety, durability and comfort. Ergonomically designed grip fits palm of hand for better control, lower effort and strain.

| CAT NO | UPC   | DESCRIPTION        | HANDLE LENGTH | STD | MSTR | WT/STD  | UNIT |
|--------|-------|--------------------|---------------|-----|------|---------|------|
| SGH2   | 24050 | 2 lb Hand Drilling | 10" Handle    | 1   | 1    | 2.440#  | Ea   |
| SGH4   | 24055 | 4 lb Hand Drilling | 10" Handle    | 1   | 1    | 5.420#  | Ea   |
| SGH8   | 24060 | 8 lb Sledge        | 32" Handle    | 1   | 1    | 8.820#  | Ea   |
| SGH10  | 24065 | 10 lb Sledge       | 32" Handle    | 1   | 1    | 11.000# | Ea   |
| SGH12  | 24080 | 12 lb Sledge       | 32" Handle    | 1   | 1    | 13.550# | Ea   |
| SGP5   | 24090 | 5 lb Pick          | 32" Handle    | 1   | 1    | 8.320#  | Ea   |

## Ground Rod Driver PC 6550

Install ground rod from ground level. Sliding action drives rod without need of hammer. Driver will not deform end of rod. Heavy duty construction provides maximum driving forces, while soft rubber ergonomic grip provides user comfort. Integral insert prevents driver from slipping off ground rod near ground level. Convenient retaining collar holds insert in tool when not in use. Can be used on all types of ground rods: copper bonded, galvanized, stainless steel, etc.

- No Need For Ladders Or Sledge Hammers!
- Heavy Duty Construction
- Completely Self Contained & Easy To Store
- Caution! Always Wear Eye Protection

| CAT NO | UPC   | DESCRIPTION                               | STD | MSTR | WT/STD  | UNIT |
|--------|-------|---|-----|------|---------|------|
| GRD58  | 24101 | 5' Driver with insert for 5/8" Ground Rod | 1   | 1    | 22.340# | Ea   |
| GRD34  | 24102 | 5' Driver with insert for 3/4" Ground Rod | 1   | 1    | 22.130# | Ea   |

### Insert Only

|        |       |                                 |   |   |        |    |
|--------|-------|---------------------------------|---|---|--------|----|
| GRDI58 | 24103 | Insert only for 5/8" Ground Rod | 1 | 1 | 5.730# | Ea |
| GRDI34 | 24104 | Insert only for 3/4" Ground Rod | 1 | 1 | 5.630# | Ea |

Our selection of wire rope dispensers, dollies, and hand totes cover most contractor needs, whether feeding wire from eight or twelve small spools on a hand tote, or cable from two 2,500 foot reels on a dolly. Our portable cable dispenser for Romex and BX is a time saver - it opens and mounts conveniently on a nearby 2 x 4 and folds for easy storage. General duty dollies are available for the economy minded. Fused powder coated yellow for durability & high visibility.



DD100B



DD101WT



DD102WT



DD104E



DD105E



DD106A

| CAT NO  | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|---------|-------|--|-----|------|--------|------|
| DD100B  | 24170 | <b>Heavy Duty Dolly</b><br>Heavy duty 10 gauge steel construction. Five 15-1/2" adjustable bars. 2 wire pulling guides inserted in the nose plate. Convenient pipe bender holder. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs.                                | 1   | 1    | 75.00# | Ea   |
| DD101WT | 24171 | <b>Heavy Duty Dolly</b><br>Heavy duty 10 gauge steel construction. Five 15-1/2" adjustable bars. 2 wire pulling guides inserted in the nose plate. Convenient pipe bender holder. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs. Includes ONE DD205HT hand tote | 1   | 1    | 79.40# | Ea   |
| DD102WT | 24172 | <b>Heavy Duty Dolly</b><br>Heavyduty 10 gauge steel construction. Five 15-1/2" adjustable bars. 2 wire pulling guides inserted in the nose plate. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs. Includes two DD205HT   | 1   | 1    | 83.80# | Ea   |
| DD104E  | 24179 | <b>General Duty Dolly</b><br>Supplied w/ five 15-1/2" adjustable/removable bars to accommodate various sizes of wire spools. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs.   | 1   | 1    | 56.00# | Ea   |
| DD105E  | 24178 | <b>General Duty Dolly</b><br>Supplied w/ five 15-1/2" adjustable/removable bars to accommodate various sizes of wire spools. supplied with ONE DD205HT. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs.  | 1   | 1    | 61.00# | Ea   |
| DD106A  | 24177 | <b>General Duty Dolly</b><br>Supplied w/ eight 18-1/2" removable bars to accommodate various sizes of wire spools. Hinge allows unit to fold flat when transporting wire. Large 10" semi-hard rubber tires for smooth handling. Will accommodate 650 lbs.  | 1   | 1    | 54.00# | Ea   |

**Hand Tote / Rope Dispenser**

|         |       |   |   |   |        |    |
|---------|-------|---|---|---|--------|----|
| DD205HT | 24174 | Hand Tote (holds 8 spools)<br>Constructed of 5/8" & 1" high strength round steel  | 1 | 1 | 4.40#  | Ea |
| DD206HT | 24181 | Hand Tote (holds 12 spools)<br>Constructed of 5/8" & 1" high strength round steel | 1 | 1 | 12.00# | Ea |
| DD207SD | 24175 | Small Wire/Rope Dispenser<br>Accepts a 14" wide reel. Post diameter is 1-7/8".    | 1 | 1 | 7.32#  | Ea |
| DD209LD | 24176 | Large Wire/Rope Dispenser<br>Accepts 19" wide reel                                | 1 | 1 | 28.58# | Ea |
| DD210R  | 24180 | Portable Cable Dispenser<br>Mounts on a 2 x 4" stud and supports 45 pounds.       | 1 | 1 | 13.75# | Ea |

**Reel Spinner**

|       |       |  |   |    |        |    |
|-------|-------|--|---|----|--------|----|
| RS896 | 17237 | Wire Dispenser assembled with 1/2" EMT | 1 | 10 | 0.490# | Ea |
|-------|-------|--|---|----|--------|----|



DD205HT



DD206HT



DD207SD



DD209LD



DD210R



RS896

# Work Gloves PC 6773

TOOLS & SPECIALTY ITEMS > WORK GLOVES > LATEX GLOVES > SHOE COVERS



Work gloves are available in a wide variety of fabrics and styles; Cotton, Canvas, Jersey (lined and Unlined), PVC Coated, Cowhide, Deerskin and Pigskin. Additionally Top Sellers include the Super Gripper, a latex dipped cool cotton glove which resists punctures, cuts and abrasions. Our Dottie exclusive line of Techwear™ a form fitting glove that is so comfortable it feels like it's a part of your hand. Techwear™ is available in three color coded styles.

| CAT NO | UPC   | SIZE        | DESCRIPTION                          | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------|--------------------------------------|-----|------|--------|------|
| GV10   | 24120 | Fits All    | Med Weight White String Knit         | 1   | 12   | 0.190# | Pair |
| GV11   | 24121 | Fits All    | 8oz Cotton Canvas, Blue Knit Wr.     | 1   | 12   | 0.190# | Pair |
| GV12   | 24122 | Fits All    | 8oz Canvas w/ PVC Dots, Knit Wr.     | 1   | 12   | 0.240# | Pair |
| GV14   | 24123 | Fits All    | Heavy Weight Brown Jersey Knit Wr.   | 1   | 12   | 0.140# | Pair |
| GV16   | 24124 | Fits All    | Brown Jersey/Red Fleece Lining       | 1   | 12   | 0.200# | Pair |
| GV20M  | 24150 | Medium      | Cotton Knit Super Gripper            | 1   | 12   | 0.210# | Pair |
| GV20L  | 24151 | Large       | Cotton Knit Super Gripper            | 1   | 12   | 0.220# | Pair |
| GV20X  | 24152 | Extra Large | Cotton Knit Super Gripper            | 1   | 12   | 0.240# | Pair |
| GV22M  | 24126 | Medium      | Leather Palm w/ Canvas Cuff          | 1   | 12   | 0.490# | Pair |
| GV22L  | 24127 | Large       | Leather Palm w/ Canvas Cuff          | 1   | 12   | 0.600# | Pair |
| GV22X  | 24128 | Extra Large | Leather Palm w/ Canvas Cuff          | 1   | 12   | 0.600# | Pair |
| GV30M  | 24129 | Medium      | Rust Split Leather Drivers           | 1   | 12   | 0.380# | Pair |
| GV30L  | 24130 | Large       | Rust Split Leather Drivers           | 1   | 12   | 0.350# | Pair |
| GV30X  | 24131 | Extra Large | Rust Split Leather Drivers           | 1   | 12   | 0.390# | Pair |
| GV35M  | 24132 | Medium      | Premium Pigskin Keystone             | 1   | 12   | 0.350# | Pair |
| GV35L  | 24133 | Large       | Premium Pigskin Keystone             | 1   | 12   | 0.350# | Pair |
| GV35X  | 24134 | Extra Large | Premium Pigskin Keystone             | 1   | 12   | 0.350# | Pair |
| GV35ML | 24148 | Medium      | Premium Pigskin Keystone Lined       | 1   | 12   | 0.370# | Pair |
| GV35LL | 24146 | Large       | Premium Pigskin Keystone Lined       | 1   | 12   | 0.370# | Pair |
| GV35XL | 24149 | Extra Large | Premium Pigskin Keystone Lined       | 1   | 12   | 0.370# | Pair |
| GV42M  | 24135 | Medium      | Top Grain Leather Drivers Pull Strap | 1   | 12   | 0.350# | Pair |
| GV42L  | 24136 | Large       | Top Grain Leather Drivers Pull Strap | 1   | 12   | 0.350# | Pair |
| GV42X  | 24137 | Extra Large | Top Grain Leather Drivers Pull Strap | 1   | 12   | 0.400# | Pair |
| GV44M  | 24138 | Medium      | Top Grain Leather Drivers            | 1   | 12   | 0.340# | Pair |
| GV44L  | 24139 | Large       | Top Grain Leather Drivers            | 1   | 12   | 0.340# | Pair |
| GV44X  | 24140 | Extra Large | Top Grain Leather Drivers            | 1   | 12   | 0.340# | Pair |
| GV52M  | 24141 | Medium      | Premium Deerskin Drivers             | 1   | 12   | 0.250# | Pair |
| GV52L  | 24142 | Large       | Premium Deerskin Drivers             | 1   | 12   | 0.280# | Pair |
| GV52X  | 24143 | Extra Large | Premium Deerskin Drivers             | 1   | 12   | 0.290# | Pair |



## Latex Gloves and Shoe Covers PC 6771



### Latex Gloves

- Superior Quality
- Resistant To Most Residual Solvents And Chemicals
- Universal Fit
- Perfect For Finish Work

### Shoe Covers

- Anti-Static
- Impervious Material
- Non-linting
- EZ On / EZ Off

| CAT NO | UPC   | DESCRIPTION             | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------------|-----|------|--------|------|
| LG100  | 59860 | 100 Latex Gloves in Jar | 1   | 10   | 2.35#  | Ea   |
| SC     | 59880 | 50 Shoe Covers in Jar   | 1   | 10   | 0.90#  | Ea   |

# Techwear™ Gloves PC 6774

- Ergo Cut Technology
- Neoprene-Spandex Laminated Back
- 100% Washable
- Charmude™ Synthetic Leather Palm For Ventilation
- Double-Stitched Schoeller® Keprotec™ Secondary Palm Layer For Positive Grip And Shock Absorption

Techwear™, a Dottie exclusive, is a form fitting glove that almost feels like part of your hand. Made with the finest materials, they are available in three color coded styles; blue for full finger lined, red for full finger unlined, and yellow for the half finger version.



| CAT NO | UPC   | SIZE     | DESCRIPTION           | COLOR  | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------|-----------------------|--------|-----|------|--------|------|
| GVT1M  | 24201 | Medium   | Full Finger (Lined)   | Blue   | 1   | 12   | 0.248# | Pair |
| GVT1L  | 24202 | Large    | Full Finger (Lined)   | Blue   | 1   | 12   | 0.248# | Pair |
| GVT1X  | 24203 | X Large  | Full Finger (Lined)   | Blue   | 1   | 12   | 0.248# | Pair |
| GVT1XX | 24204 | XX Large | Full Finger (Lined)   | Blue   | 1   | 12   | 0.248# | Pair |
| GVT2M  | 24207 | Medium   | Full Finger (Unlined) | Red    | 1   | 12   | 0.248# | Pair |
| GVT2L  | 24208 | Large    | Full Finger (Unlined) | Red    | 1   | 12   | 0.248# | Pair |
| GVT2X  | 24209 | X Large  | Full Finger (Unlined) | Red    | 1   | 12   | 0.248# | Pair |
| GVT2XX | 24210 | XX Large | Full Finger (Unlined) | Red    | 1   | 12   | 0.248# | Pair |
| GVT3M  | 24213 | Medium   | Half Finger (Unlined) | Yellow | 1   | 12   | 0.180# | Pair |
| GVT3L  | 24214 | Large    | Half Finger (Unlined) | Yellow | 1   | 12   | 0.180# | Pair |
| GVT3X  | 24215 | X Large  | Half Finger (Unlined) | Yellow | 1   | 12   | 0.180# | Pair |
| GVT3XX | 24216 | XX Large | Half Finger (Unlined) | Yellow | 1   | 12   | 0.180# | Pair |

## Hybrid Gloves PC 6774

### Goatskin With Safety Cuff:

- Safety Cotton Cuff
- Premium Suede Palm
- Keystone Thumb With Gusset Stitching
- Neoprene-padded Knuckle
- Breathable Spandex Back
- Stretchable Lycra Side Panels In Glove Fingers

### Deerskin With Neoprene Cuff:

- Neoprene Cuff
- Top Grain Deerskin Leather
- Keystone Thumb With Gusset Stitching
- Breathable Spandex Back
- Reinforced Leather Patches
- Stretchable Lycra Side Panels In Glove Fingers

The durability of traditional leather work gloves combined with the advanced materials of high performance dexterity gloves.



| CAT NO | UPC   | SIZE    | DESCRIPTION                 | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------|-----------------------------|-----|------|--------|------|
| GV270M | 81039 | Medium  | Goatskin With Safety Cuff   | 1   | 12   | 0.24#  | Pair |
| GV270L | 81040 | Large   | Goatskin With Safety Cuff   | 1   | 12   | 0.24#  | Pair |
| GV270X | 81041 | X Large | Goatskin With Safety Cuff   | 1   | 12   | 0.24#  | Pair |
| GV285M | 81042 | Medium  | Deerskin With Neoprene Cuff | 1   | 12   | 0.24#  | Pair |
| GV285L | 81043 | Large   | Deerskin With Neoprene Cuff | 1   | 12   | 0.24#  | Pair |
| GV285X | 81044 | X Large | Deerskin With Neoprene Cuff | 1   | 12   | 0.24#  | Pair |

## TECH TALK

### Techwear™ Gloves

Posi-Grip™ non-slip cradle for sure grip and control when handling tools

Neoprene/Spandex™ laminated back

- Neoprene gives soft padded protection to the back of hand.
- The breathable Spandex™ ventilates to keep hands cool and flexes for a snug, comfortable fit.
- Full-finger, Full-finger lined, and Half-finger versions available
- 100% washable



Chamude™ synthetic leather palm absorbs moisture, ventilates and provides both excellent sensitivity and abrasion resistance

Double-stitched Schoeller® Keprotec™ secondary palm layer for positive grip and shock absorption

See new products at [Ihdottie.com](http://Ihdottie.com)

Dottie

E31

TOOLS & SPECIALTY ITEMS > TECHWEAR GLOVES > HYBRID GLOVES

Tool Holders, Organizers & Accessories  
PC 6770



- 5" Padded Comfort Belt - Universal And In Sizes
- Nylon Stitching & Double Steel Rivets Reinforce Major Stress Points
- New Larger Screw Driver Holders
- Jumbo Pockets With Meter/Phone Clip
- 2" Double Tongue Metal Roller Buckle


| CAT NO    | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|-----------|-------|---|-----|------|--------|------|
| YF520EU   | 11972 | <b>Universal</b> 5" Back Support 23-large pockets w/ meter clip & top handles. Sm, Med & Lg | 1   | 3    | 2.34#  | Ea   |
| YF520ES   | 11949 | <b>Small Size</b> 5" Back Support 23-large pockets w/ meter clip & top handles 29"- 34"     | 1   | 3    | 2.69#  | Ea   |
| YF520EM   | 11944 | <b>Medium Size</b> 5" Back Support 23-large pockets w/ meter clip & top handles 35"- 39"    | 1   | 3    | 2.89#  | Ea   |
| YF520EL   | 11945 | <b>Large Size</b> 5" Back Support 23-large pockets w/ meter clip & top handles 40"- 46"     | 1   | 3    | 2.94#  | Ea   |
| YF520EXL  | 11946 | <b>X Large Size</b> 5" Back Support 23-large pockets w/ meter clip & top handles 46"- 56"   | 1   | 3    | 2.95#  | Ea   |
| YE5WBNU   | 11973 | <b>Universal</b> 5" Back Support Comfort Belt Accommodates sizes; Sm, Med & Lg              | 1   | 3    | 0.96#  | Ea   |
| YE5WBNS   | 11948 | <b>Small Size</b> 5" Back Support Comfort Belt 29"- 34"                                     | 1   | 3    | 0.75#  | Ea   |
| YE5WBNSM  | 11936 | <b>Medium Size</b> 5" Back Support Comfort Belt 35"- 39"                                    | 1   | 3    | 0.85#  | Ea   |
| YE5WBNSL  | 11937 | <b>Large Size</b> 5" Back Support Comfort Belt 40"- 46"                                     | 1   | 3    | 0.91#  | Ea   |
| YE5WBNSXL | 11938 | <b>X Large Size</b> 5" Back Support Comfort Belt 46"- 56"                                   | 1   | 3    | 0.94#  | Ea   |



Climate Gear Tool Holders  
PC 6770

Put a layer of heavy duty, weather-resistant tarpaulin between your tools and the harsh weather outside. Climate Gear keeps tools and accessories out of the elements, wherever the job takes you.

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| YH1205 | 81034 | 9" Soft Tool Bag<br>9" L x 2-1/4" W x 6-1/4" H<br>Durable interwoven tarpaulin construction. Weather resistant zippers. Polyester bottom w/rubber strips. Organizes hand tools, parts, bits & fasteners.   | 1   | 3    | 0.45#  | Ea   |
| YH1206 | 81035 | 12" Large Parts Bag<br>12" L x 3" W x 8" H<br>Durable interwoven tarpaulin construction. Weather resistant zippers. Polyester bottom with rubber strips. Organizes hand tools, parts, bits & fasteners.  | 1   | 3    | 0.60#  | Ea   |
| YH1258 | 81037 | 14" Soft Tool Bag<br>14" L x 9-1/2" W x 11" H<br>Durable interwoven tarpaulin construction. Weather resistant zippers. Polyester bottom with rubber strips. Padded anti-slip shoulder strap with metal clips. Large internal compartment with 12 webbing tool loops and pockets. Large external zipper compartment & front tool cover    | 1   | 3    | 3.65#  | Ea   |
| YH1263 | 81038 | 18" Soft Tool Bag<br>18" L x 10-1/2" W x 12" H<br>Durable interwoven tarpaulin construction. Weather resistant zippers. Polyester bottom with rubber strips. Padded anti-slip shoulder strap with metal clips. Large internal compartment with 12 webbing tool loops and pockets. Large external zipper compartment and front tool cover | 1   | 3    | 3.75#  | Ea   |
| YH1213 | 81036 | Bucket Tool Bag<br>11-1/2" Round x 14" H<br>Durable interwoven tarpaulin construction. Unique dome top with weather resistant zipper. 20 internal pockets. 12" diameter internal compartment reinforced with 600D polyester. Adjustable metal frame partition slides into place. Polyester bottom with rubber strips                     | 1   | 3    | 4.60#  | Ea   |



- Ballistic Nylon Bindings And Grip Strip™ Hook And Loop Fastener System Keeps Pouches In Place
- Double Layer Lightweight Nylon Will Not Crack, Harden Or Mildew
- Nylon Stitching & Double Steel Rivets Reinforce Major Stress Points
- All Parts Are Removable & Interchangeable

Need proof positive that something doesn't have to be made of leather to be tough and durable? Look no further than Dottie's lineup of hard working, hard wearing, nylon tool bags, featuring stay open pockets. Softside Tool carriers include handy tote trays and are just one of the creative touches you'll find in our product line.



| CAT NO | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| YA1148 | 11900 | 22-Pocket, Drawstring BucketBag™<br>10" Round x 6" High   | 1   | 3    | 0.850# | Ea   |
| YB1132 | 11913 | 75-Pocket Backpack<br>13" W x 17-1/2" H x 9" D Closed.<br>Deluxe back pack w/ multi-comp.   | 1   | 3    | 5.200# | Ea   |
| YB1137 | 11909 | 12-Pocket Traytote™ Bag<br>12" L x 8" W x 12" H Multi-compartment.<br>Plastic tray included, 11" X 6"   | 1   | 3    | 3.600# | Ea   |
| YB1139 | 11914 | 14-Pocket, Large Traytote™ Bag<br>2 Pockets inside, 12 outside. 13-1/2" x 6"<br>multi-compartment plastic tray included   | 1   | 3    | 5.330  | Ea   |
| YB1141 | 11915 | 37-Pocket, double Traytote™ Bag<br>2 Pockets inside, 35 outside. Double 11" x 6"<br>multi-compartment, plastic trays included   | 1   | 3    | 7.960# | Ea   |
| YB1164 | 11911 | 32-Pocket, 24" Megamouth™ Tote bag<br>24" L x 11" W x 12" H   | 1   | 3    | 4.610# | Ea   |
| YB1526 | 11917 | 28-Pocket Electrical & Maintenance Tool Pouch<br>7" x 5-1/2" multi-compartment.<br>Plastic tray included  | 1   | 3    | 3.240# | Ea   |
| YB1529 | 11993 | 15 Pocket 16" Center Tray Tool Bag<br>13-1/2" x 9" multi-compartment plastic tray<br>included. 8 pockets outside and 7 inside to<br>organize tools and accessories      | 1   | 3    | 4.330# | Ea   |
| YB1530 | 11919 | 43 Pockets w/ Plastic Tray<br>Window pockets & shoulder strap<br>23" L x 12" W x 15" H  | 1   | 3    | 4.720# | Ea   |
| YB1534 | 11870 | 16" Tote Bag with Tray<br>10 pockets inside, 13 pockets outside.<br>10" x 3" multi-compartment plastic tray.<br>Reinforced web carrying handles<br>16" L x 8" W x 11" H | 1   | 3    | 5.550# | Ea   |
| YB1535 | 11871 | 18" Tote Bag with Tray<br>13 Pockets inside, 24 pockets outside.<br>13-1/2" x 3" multi-compartment tray.<br>Reinforced web carrying handles.<br>18" L x 11" W x 11" H   | 1   | 3    | 5.650# | Ea   |





| CAT NO | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| YB1537 | 11872 | 13" Multi-Compartment Tool Carrier<br>23 Pockets inside and 10 pockets outside.<br>Zippered side panel.Padded, reinforced web<br>carrying handles. 13" L x 7" W x 13" H                       | 1   | 3    | 3.75#  | Ea   |
| YB1544 | 11873 | 18" Tote Bag w/Swivel Parts Organizer<br>14 Multi-use outside pockets, 8 inside pockets.<br>Padded web carrying handle.Double swivel<br>plastic organizer. 18" L x 9" W x 11-1/2"H            | 1   | 3    | 6.35#  | Ea   |
| YB1570 | 11874 | 12" Soft-sided Tool Box<br>12 Multi-use outside pockets, 8 inside. Padded<br>web carrying handle. Multi-compartment plastic.<br>Screen mesh zippered pocket. 12" L x 8-1/2" W x 14" H         | 1   | 3    | 4.50#  | Ea   |
| YB1572 | 11875 | 18" Soft-sided Tool Box<br>21 Multi-use outside pockets, 12 inside. Padded<br>rubber web carrying handle. 8" x 4" Multi-compartment<br>plastic tray. Large interior. 18" L x 9-1/2" W x 14" H | 1   | 3    | 4.40#  | Ea   |
| YB1581 | 81914 | 15" Open Top Tool Bag with molded base.<br>12 external pockets, including 2 oversized pockets.<br>Interior includes additional pockets.<br>15" L x 8" W x 9-3/4" H                            | 1   | 3    | 4.00#  | Ea   |
| YB1582 | 81915 | 15" Zipper Top Tool Carrier with molded base.<br>Exclusive tray system for small parts and accessories.<br>12 external pockets and 8 inside pockets.<br>15" L x 8-1/2" W x 12-1/2" H          | 1   | 3    | 4.00#  | Ea   |
| YD2PS  | 11939 | 2" Wide Padded Work Suspenders - Black  | 1   | 3    | 0.66#  | Ea   |
| YC361  | 11974 | UltraFlex® Professional Kneepad<br>Gel center provides maximum cushioning.<br>Adjustable rubber straps. One size fits all.  | 1   | 3    | 1.73#  | Pair |
| YC345  | 11975 | Professional Kneepad<br>SuperThick High Density foam for maximum<br>comfort. Two strap fastening adds stability.  | 1   | 3    | 1.37#  | Pair |
| YG1101 | 11926 | 3 Multi-purpose Clip-on, Zippered Bags<br>Blue - 9" x 7"; Green - 7" x 6"; Red 6" x 5".<br>All w/durable clip hanger.   | 1   | 3    | 0.35#  | Ea   |
| YG1104 | 11966 | 4 Pocket Multi-purpose Tool Holder  |     |      |        |      |
| YG1108 | 11994 | 3 Multi-purpose Clip Bag Combo<br>One ea; 4" x 3" x 9", 3-1/2" x 2-1/2" x 8"<br>3" x 2" x 6-1/2". Easy-lock/push button-released<br>draw string system.                                       | 1   | 3    | 0.67#  | Ea   |
| YG5124 | 11963 | Universal Cell Phone Holder (Small)<br>Specially designed for small cell phones.<br>Versatile 2-way attachment for belts, pants,<br>etc. Heavy duty clip.                                     | 1   | 3    | 0.15#  | Ea   |
| YG5127 | 11961 | Large Cell Phone Holster<br>Hang-strap-clip onto work belts,suspenders, pants,<br>etc. Holds most brands of large cell phones.  | 1   | 3    | 0.17#  | Ea   |





| CAT NO  | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|---------|-------|---|-----|------|--------|------|
| YG5539  | 11962 | Steel Loop Hammer Holder<br>Made of durable fabric.<br>Cradle design prevents hammer pivoting.<br>Fits belts up to 2-3/4" wide.   | 1   | 3    | 0.21#  | Ea   |
| YF11ENP | 11940 | 11-pocket new larger<br>Professional Electrician's Tool Pouch,<br>nylon E-Z carry handles   | 1   | 3    | 0.99#  | Ea   |
| YF6DH   | 11947 | 12-pocket new wider & taller<br>Electrician's Pouch With Hammer Loop,<br>nylon E-Z carry handles  | 1   | 3    | 1.02#  | Ea   |
| YF7EN   | 11942 | 7-Pocket Electrician's Tool Pouch nylon   | 1   | 3    | 0.76#  | Ea   |
| YF5508  | 11928 | 20-pocket Pro Electrician's Tool Pouch<br>with shoulder strap, 6 large screwdriver<br>holders 1 steel hammer holder, grip-strip<br>hook & loop fastening system                 | 1   | 3    | 1.50#  | Ea   |
| YF1509  | 11992 | 21-pocket zippered Professional Electrician's<br>Tool Pouch. Rubber handle and padded<br>shoulder strap designed for easy storage.<br>Outside pocket to hold cell phone holder. | 1   | 3    | 2.67#  | Ea   |
| YG5169  | 11927 | Clip-on Window Pocket with heavy duty clip<br>Hook and loop top closure   | 1   | 3    | 0.33#  | Ea   |
| YG4MN   | 11959 | Electrical Meter/Tester/Phone Holder<br>Medium, nylon 4 1/2" H x 2-1/2" W x 1-1/2" D  | 1   | 3    | 0.23#  | Ea   |
| YG6MN   | 11960 | Electrical Meter/Tester/Phone Holder<br>Large, nylon 6" H x 3" W x 2" D   | 1   | 3    | 0.31#  | Ea   |
| YF5050  | 11950 | 3 Piece Comfortfit Electricians Combo<br>with added support belt  | 1   | 3    | 3.54#  | Ea   |



**Sharpie® Holder  
PC 6770**



- Constructed of Heavy Duty Webbing
- Heavy Duty Belt Clip
- Die Cast Cap
- Webbing Prevents Accidental Marking of User's Clothing

Marking pens are used by professional contractors every day. Our new Kwik-Draw Holster eliminates the awkward task of removing and replacing the cap of a marking pen for each use and keeps the pen handy at your side. Simply discard the cap the pen came with and use the precision grip cap affixed to the holster. Turns a two handed task into a one hand task.



| CAT NO | UPC   | DESCRIPTION     | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------------|-----|------|--------|------|
| SH     | 81893 | Sharpie® Holder | 1   | 10   | 0.23#  | Ea   |

## Rope Lock Tie Down System PC 6776



- Patented Quick Release Rope Lock
- Stainless Steel Lever Spring
- Zinc Plated Hooks
- Sonic Welded Construction
- Easy Thumb Release
- Non-corrosive
- Fully Assembled & Ready to Use

| CAT NO | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| RTL10  | 17238 | Rope Lock Tie Down System 10' Green and White 3/8" Braided Polypropylene Rope | 1   | 12   | 0.500# | Ea   |



## Web Straps (Tie Down) PC 6775




- Weatherproof
- 750 lb. Test Webbing
- Strong 1" Heavy Duty Web Construction
- Rustproof, Cam-Action Buckle
- For Securing Contractor, DIY, Landscape Maintenance, Recreational Loads
- Available In 2 Piece Bag Or Counter Merchandiser
- 6 Color Coded Lengths: 2 Ft. To 12 Ft.
- Individual Lengths May Be Re-ordered In 1 Dozen Quantities
- Display Box Comes With Header Card
- Caution! Always Wear Eye Protection

WS00 Contains: 36 Web Straps (6 of Ea. Length)

| CAT NO | UPC   | DESCRIPTION                   | COLOR    | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------------------------------|----------|-----|------|--------|------|
| WS00   | -     | Counter Merchandiser w/Straps | Assorted | 1   | 1    | 6.80#  | Ea   |
| WS02   | 24160 | 2' Nylon Tie Down w/Buckle    | Red      | 12  | 144  | 2.05#  | Ea   |
| WS04   | 24161 | 4' Nylon Tie Down w/Buckle    | Yellow   | 12  | 144  | 2.45#  | Ea   |
| WS06   | 24162 | 6' Nylon Tie Down w/Buckle    | Green    | 12  | 144  | 2.90#  | Ea   |
| WS08   | 24163 | 8' Nylon Tie Down w/Buckle    | Purple   | 12  | 144  | 3.35#  | Ea   |
| WS10   | 24164 | 10' Nylon Tie Down w/Buckle   | Blue     | 12  | 144  | 3.75#  | Ea   |
| WS12   | 24165 | 12' Nylon Tie Down w/Buckle   | Black    | 12  | 144  | 4.05#  | Ea   |

### Strap-It 2 Pc Hang-up Display Pack

|       |       |                             |        |   |    |       |         |
|-------|-------|-----------------------------|--------|---|----|-------|---------|
| 2WS02 | 58211 | 2' Nylon Tie Down w/Buckle  | Red    | 1 | 12 | 2.05# | Ea Pack |
| 2WS04 | 58212 | 4' Nylon Tie Down w/Buckle  | Yellow | 1 | 12 | 2.45# | Ea Pack |
| 2WS06 | 58213 | 6' Nylon Tie Down w/Buckle  | Green  | 1 | 12 | 2.90# | Ea Pack |
| 2WS08 | 58214 | 8' Nylon Tie Down w/Buckle  | Purple | 1 | 12 | 3.35# | Ea Pack |
| 2WS10 | 58215 | 10' Nylon Tie Down w/Buckle | Blue   | 1 | 12 | 3.75# | Ea Pack |
| 2WS12 | 58216 | 12' Nylon Tie Down w/Buckle | Black  | 1 | 12 | 4.05# | Ea Pack |



Heavy-use Strap-it tie-down straps are now available in 6 popular color-coded lengths.