



GFCIs

 **legrand**[®]

Pass & Seymour

P&S innovations – from the first GFCI receptacle to SafeLock™ Protection.



In 1971, we introduced the first GFCI receptacle. Soon, our invention was preventing injuries and saving lives throughout North America.

That spirit of innovation and commitment to safety continues. P&S GFCI receptacles now have SafeLock™ Protection – and made it standard in all our GFCI receptacles. It goes beyond UL® standards to provide our best GFCI safety ever. With SafeLock Protection, if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

Today, you'll find P&S innovation and safety throughout a broad range of GFCI products – products that offer new versatility, save installation time, and solve problems. And products that continue a proud safety tradition that we began more than 30 years ago.

A full range of intelligently engineered, highly durable, and reliable GFCIs — whether you require receptacle, combination, portable, or in-line ground fault protection.

Index

Device	Rating	Page Number
TradeMaster® & Specification Grade GFCI Receptacles	15 & 20A, 125VAC	C-2, C-5
Tamper-Resistant GFCI Receptacles	15 & 20A, 125VAC	C-3
Hospital Grade Tamper-Resistant GFCI Receptacles	15 & 20A, 125VAC	C-4
Hospital Grade GFCI Receptacles	15 & 20A, 125VAC	C-6
Illuminated GFCI Receptacles	20A, 125VAC	C-7
Specification Grade Dead Front GFCIs	20A, 125VAC	C-8
Decorator Combination Tamper-Resistant Switch/GFCI Receptacles	15A, 125VAC	C-9
Decorator Combination Tamper-Resistant Nightlight/GFCI Receptacles	15 & 20A, 125VAC	C-10
Weather-Resistant GFCI Receptacles	15 & 20A, 125VAC	C-11
Weather-Resistant DuraShield™ GFCI Receptacles	15 & 20A, 125VAC	C-12
PlugTail™ Specification Grade GFCI Receptacles	15 & 20A, 125VAC	C-13
PlugTail™ Hospital Grade GFCI Receptacles	15 & 20A, 125VAC	C-14
PlugTail™ Tamper-Resistant GFCI Receptacles	15 & 20A, 125VAC	C-15
PlugTail™ Tamper-Resistant Nightlight/GFCI Receptacles	15 & 20A, 125VAC	C-16
NAFTA-Compliant & RoHS-Compliant GFCI Receptacles	15 & 20A, 125VAC	C-17, C-18
NAFTA-Compliant PlugTail™ GFCI Receptacles	15 & 20A, 125VAC	C-19, C-20
GFCI Portables		C-21 – C-23



Pass & Seymour

GFCIs TradeMaster® & Specification Grade GFCI Receptacles

GFCIs with patented SafeLock™ Protection
If critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Back wire clamp allows for fast installation of ground wires.



Trip indicator light (LED) makes it easy to identify tripped condition.

Captive screws make for easier installation.

Two back wire holes per termination add wiring flexibility, eliminate pigtailing, and save box space.

Extra-long strap for better sheet rock contact eliminates “floaters” yet takes standard wall plate.

1595LA

Side or internal screw-pressure-plate back wire termination takes #10–#14 AWG stranded or solid, copper or copper-clad conductors.

1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.

The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.

FSUL Listed (Federal Specification WC596).



Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

GFCIs

Tamper-Resistant GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

GFCIs

Features	
<ul style="list-style-type: none"> ■ Protects children: patented shutter system helps prevent improper insertion of foreign objects. ■ Meets National Electrical Code® Tamper-Resistant requirements. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ FSUL Listed (Federal Specification WC596). ■ Trip indicator light (red LED). ■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. 	<ul style="list-style-type: none"> ■ Two back wire holes per terminal. ■ Ground screw has a back wire clamp for easy installation. ■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Extra-long strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity





1595TRW



2095TRSW

Catalog Number	Rating A. VAC		Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI							
1595TRI	15	125	Ivory	5-15R	•	•	•
1595TRW	15	125	White	5-15R	•	•	•
1595TR	15	125	Brown	5-15R	•	•	•
1595TRBK	15	125	Black	5-15R	•	•	•
1595TRLA	15	125	Light Almond	5-15R	•	•	•
1595TRBNCC4	15	125	Brushed Nickel	5-15R	•	•	•
1595TRTI	15	125	Titanium	5-15R	•	•	•
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI with Auto-Ground							
1595TRSI	15	125	Ivory	5-15R	•	•	•
1595TRSW	15	125	White	5-15R	•	•	•
1595TRSLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI							
2095TRI	20	125	Ivory	5-20R	•	•	•
2095TRW	20	125	White	5-20R	•	•	•
2095TR	20	125	Brown	5-20R	•	•	•
2095TRGRY	20	125	Gray	5-20R	•	•	•
2095TRBK	20	125	Black	5-20R	•	•	•
2095TRRED	20	125	Red	5-20R	•	•	•
2095TRLA	20	125	Light Almond	5-20R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI with Auto-Ground							
2095TRSI	20	125	Ivory	5-20R	•	•	•
2095TRSW	20	125	White	5-20R	•	•	•
2095TRSLA	20	125	Light Almond	5-20R	•	•	•



National Electrical Code® Section 406.11 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Tamper-Resistant GFCI Receptacles




Pass & Seymour

GFCIs Hospital Grade Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595HGTRW



2095HGTRW



Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Hospital Grade Tamper-Resistant 15 Amp Duplex GFCI						
1595HGTRI	15 125	Ivory	5-15R	•	•	•
1595HGTRW	15 125	White	5-15R	•	•	•
1595HGTR	15 125	Brown	5-15R	•	•	•
1595HGTRGRY	15 125	Gray	5-15R	•	•	•
1595HGTRRED	15 125	Red	5-15R	•	•	•
1595HGTRLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI						
2095HGTRI	20 125	Ivory	5-20R	•	•	•
2095HGTRW	20 125	White	5-20R	•	•	•
2095HGTR	20 125	Brown	5-20R	•	•	•
2095HGTRGRY	20 125	Gray	5-20R	•	•	•
2095HGTRRED	20 125	Red	5-20R	•	•	•
2095HGTRLA	20 125	Light Almond	5-20R	•	•	•




GFCIs TradeMaster® & Specification Grade GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Features	
<ul style="list-style-type: none"> SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED). Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. Ground screw has a back wire clamp for easy installation. 	<ul style="list-style-type: none"> 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Mounting screws are shipped captive in the device and wall plate for easier installation. High-impact-resistant thermoplastic construction. Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws. GFCIs with Auto-Ground assure a positive ground to metal box.
Specifications	
<ul style="list-style-type: none"> Supply Voltage: 125VAC, 60 Hz Supply Voltage Range: 102-132 VAC Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> Trip Time: 0.025 sec., nominal per UL Standard 20 Amp feed-thru capacity



1595W



1595SW



2095W



NEMA 5-15R



NEMA 5-20R

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade 15 Amp Duplex GFCI							
1595I	15	125	Ivory	5-15R	•	•	•
1595W	15	125	White	5-15R	•	•	•
1595	15	125	Brown	5-15R	•	•	•
1595GRY	15	125	Gray	5-15R	•	•	•
1595BK	15	125	Black	5-15R	•	•	•
1595RED	15	125	Red	5-15R	•	•	•
1595LA	15	125	Light Almond	5-15R	•	•	•
TradeMaster®/Spec Grade 15 Amp Duplex GFCI with Auto-Ground							
1595SI	15	125	Ivory	5-15R	•	•	•
1595SW	15	125	White	5-15R	•	•	•
1595SLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI							
2095I	20	125	Ivory	5-20R	•	•	•
2095W	20	125	White	5-20R	•	•	•
2095	20	125	Brown	5-20R	•	•	•
2095GRY	20	125	Gray	5-20R	•	•	•
2095BK	20	125	Black	5-20R	•	•	•
2095RED	20	125	Red	5-20R	•	•	•
2095LA	20	125	Light Almond	5-20R	•	•	•
Specification Grade 20 Amp Duplex GFCI with Auto-Ground							
2095SI	20	125	Ivory	5-20R	•	•	•
2095SW	20	125	White	5-20R	•	•	•
2095SLA	20	125	Light Almond	5-20R	•	•	•


All devices listed on this page conform to NEMA WD-1 and WD-6.




Pass & Seymour

GFCIs Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595HGW



2095HGW

Features

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI							
1595HGI	15	125	Ivory	5-15R	•	•	•
1595HGW	15	125	White	5-15R	•	•	•
1595HG	15	125	Brown	5-15R	•	•	•
1595HGGRY	15	125	Gray	5-15R	•	•	•
1595HGRED	15	125	Red	5-15R	•	•	•
1595HGLA	15	125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI							
2095HGI	20	125	Ivory	5-20R	•	•	•
2095HGW	20	125	White	5-20R	•	•	•
2095HG	20	125	Brown	5-20R	•	•	•
2095HGGRY	20	125	Gray	5-20R	•	•	•
2095HGRED	20	125	Red	5-20R	•	•	•
2095HGLA	20	125	Light Almond	5-20R	•	•	•



NEMA 5-15R



NEMA 5-20R


GFCIs

Illuminated GFCI Receptacles

2 Pole, 3 Wire Grounding 20A, 125VAC




Features	
<ul style="list-style-type: none"> ■ Green indicator light (LED) is ON when power is available. Helps identify emergency power branch circuits. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ FSUL Listed (Federal Specification WC596). ■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. ■ Two back wire holes per terminal. 	<ul style="list-style-type: none"> ■ Ground screw has a back wire clamp for easy installation. ■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Extra-long strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity



2095HGWL

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL _{US} UL943 C22.2 No. 144	cUL _{US} UL498 C22.2 No. 42	FSUL WC596
Specification Grade Illuminated 20 Amp Duplex GFCI							
2095IL	20	125	Ivory	5-20R	•	•	•
2095WL	20	125	White	5-20R	•	•	•
2095LAL	20	125	Light Almond	5-20R	•	•	•
Hospital Grade Illuminated 20 Amp Duplex GFCI							
2095HGIL	20	125	Ivory	5-20R	•	•	•
2095HGWL	20	125	White	5-20R	•	•	•
2095HGREDL	20	125	Red	5-20R	•	•	•





Pass & Seymour

GFCIs Specification Grade Dead Front GFCI

20A, 125VAC



2085W

Features

- Rated as a 1½ HP motor control switch.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to the load is disconnected.
- Prevents line-load reversal miswire: no power to the load or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz.
- Supply Voltage Range: 102-132 VAC.
- Trip Threshold: 5± 1mA.
- Trip Time: 0.025 sec., nominal per UL Standard.
- 20 Amp feed-thru capacity.

Catalog Number	Rating		Color	3rd Party Compliance	
	A.	VAC		UL943 C22.2 No. 144	UL508 C22.2 No. 14
Specification Grade Dead Front GFCI – 1½ HP Motor Control Rating					
2085I	20	125	Ivory	•	•
2085W	20	125	White	•	•
2085BK	20	125	Black	•	•
2085LA	20	125	Light Almond	•	•


Catalog Number	Description
Accessories – GFCIs	
1594TPAI	7.0 cu. in. Extension Ring, Ivory
1594TPAW	7.0 cu. in. Extension Ring, White
1594TPA	7.0 cu. in. Extension Ring, Brown
1594TPALA	7.0 cu. in. Extension Ring, Light Almond

GFCIs Decorator Combination Tamper-Resistant Switch/GFCI Receptacles

15A, 125VAC




Features	
<ul style="list-style-type: none"> ■ Protects children: patented shutter system helps prevent improper insertion of foreign objects. ■ Meets National Electrical Code® Tamper-Resistant requirements. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ Up-down switching. ■ 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals. ■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ Trip indicator light (red LED). ■ Two back wire holes per terminal. 	<ul style="list-style-type: none"> ■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. ■ Ground screw has a back wire clamp for easy installation. ■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Extra-long strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity




1595SWTTRWCC4

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	cUL ^{us} UL20 C22.2 No. 111
Combination Tamper-Resistant Single Pole Switch/GFCI							
1595SWTTRICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595SWTTRWCC4	15 120	15 125	White	5-15R	•	•	•
1595SWTTRBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595SWTTRLACC4	15 120	15 125	Light Almond	5-15R	•	•	•






Pass & Seymour



1595NTLTRWCC4



2095HGNTLTRW



NEMA 5-15R



NEMA 5-20R

GFCIs Decorator Combination Tamper-Resistant Nightlight/GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Two receptacles.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- Trip Threshold: 5± 1mA
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance		
					cUL943 UL943 C22.2 No. 144	cUL498 UL498 C22.2 No. 42	FSUL WC596
Combination Tamper-Resistant 15 Amp Nightlight/GFCI							
1595NTLTRICC4	15 125	0.180	Ivory	5-15R	•	•	•
1595NTLTRWCC4	15 125	0.180	White	5-15R	•	•	•
1595NTLTRBKCC4	15 125	0.180	Black	5-15R	•	•	•
1595NTLTRLACC4	15 125	0.180	Light Almond	5-15R	•	•	•
1595NTLTRBNCC4	15 125	0.180	Brushed Nickel	5-15R	•	•	•
1595NTLTRTICC4	15 125	0.180	Titanium	5-15R	•	•	•
Combination Tamper-Resistant 20 Amp Nightlight/GFCI							
2095NTLTRI	20 125	0.180	Ivory	5-20R	•	•	•
2095NTLTRW	20 125	0.180	White	5-20R	•	•	•
2095NTLTRGRY	20 125	0.180	Gray	5-20R	•	•	•
2095NTLTRLA	20 125	0.180	Light Almond	5-20R	•	•	•
Hospital Grade Combination Tamper-Resistant 15 Amp Nightlight/GFCI							
1595HGNTLTRI	15 125	0.180	Ivory	5-15R	•	•	•
1595HGNTLTRW	15 125	0.180	White	5-15R	•	•	•
1595HGNTLTR	15 125	0.180	Brown	5-15R	•	•	•
1595HGNTLTRGRY	15 125	0.180	Gray	5-15R	•	•	•
1595HGNTLTRRED	15 125	0.180	Red	5-15R	•	•	•
1595HGNTLTRLA	15 125	0.180	Light Almond	5-15R	•	•	•
Hospital Grade Combination Tamper-Resistant 20 Amp Nightlight/GFCI							
2095HGNTLTRI	20 125	0.180	Ivory	5-20R	•	•	•
2095HGNTLTRW	20 125	0.180	White	5-20R	•	•	•
2095HGNTLTRGRY	20 125	0.180	Gray	5-20R	•	•	•
2095HGNTLTRRED	20 125	0.180	Red	5-20R	•	•	•
2095HGNTLTRLA	20 125	0.180	Light Almond	5-20R	•	•	•

*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page S-56 for more information.

All devices listed on this page conform to NEMA WD-1 and WD-6.

GFCIs

Weather-Resistant GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

GFCIs

Features	
<ul style="list-style-type: none"> ■ Weather-Resistant: Meets National Electrical Code® Weather-Resistant requirements. ■ Tamper-Resistant: Meets National Electrical Code® Tamper-Resistant requirements. ■ Protects children: patented shutter system helps prevent improper insertion of foreign objects. ■ Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: <ul style="list-style-type: none"> - Ultraviolet light exposure test - Cold impact test - Accelerated aging test - Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. 	<ul style="list-style-type: none"> ■ FSUL Listed (Federal Specification WC596). ■ Trip indicator light (red LED). ■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. ■ Two back wire holes per terminal. ■ Ground screw has a back wire clamp for easy installation. ■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Extra-long nickel post-plated steel mounting strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity





1595TRWRW



2095TRWRW

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				cUL _{US} UL943 C22.2 No. 144	cUL _{US} UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade Weather-Resistant 15 Amp Duplex GFCI						
1595TRWRI	15 125	Ivory	5-15R	•	•	•
1595TRWRW	15 125	White	5-15R	•	•	•
1595TRWR	15 125	Brown	5-15R	•	•	•
1595TRWRLA	15 125	Light Almond	5-15R	•	•	•
Specification Grade Weather-Resistant 20 Amp Duplex GFCI						
2095TRWRI	20 125	Ivory	5-20R	•	•	•
2095TRWRW	20 125	White	5-20R	•	•	•
2095TRWR	20 125	Brown	5-20R	•	•	•
2095TRWRGRY	20 125	Gray	5-20R	•	•	•
2095TRWRLA	20 125	Light Almond	5-20R	•	•	•



National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.


Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Weather-Resistant GFCI Receptacles



Pass & Seymour



1595DSWRBKCC4



GFCIs Weather-Resistant DuraShield™ GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



Features

- Designed for extra durability and a long service life when installed in harsh environments: outdoor, garages, workshops, wash down areas, commercial kitchens, and labs.
- Weather-Resistant: Meets National Electrical Code® Weather-Resistant requirements.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including:
 - Ultraviolet light exposure test
 - Cold impact test
 - Accelerated aging test
 - Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- Dust- and insect-resistant.
- Rubber curtains let plug blades in; keep dust, water and insects out.
- Integral gasket seals receptacle, protecting critical electronic components.
- Exceeds UL corrosion requirements – survives 4X the required corrosion test cycles.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long nickel post-plated steel mounting strap.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance	
				cUL943 UL943 C22.2 No. 144	cUL498 UL498 C22.2 No. 42
Specification Grade Weather-Resistant DuraShield™ 15 Amp Duplex GFCI					
1595DSWRBKCC4	15 125	Black	5-15R	•	•
Specification Grade Weather-Resistant DuraShield™ 20 Amp Duplex GFCI					
2095DSWRBK	20 125	Black	5-20R	•	•



National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.

Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

GFCIs

PlugTail™ Specification Grade GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



Pass & Seymour

GFCIs

Features	
<ul style="list-style-type: none"> ■ Faster, more reliable installation. ■ No exposed terminals create a finger safe application before, during, and after installation. ■ Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector. ■ GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ FSUL Listed (Federal Specification WC596). 	<ul style="list-style-type: none"> ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ Trip indicator light (red LED). ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Zinc-plated steel mounting strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity



PT2095W




Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL _{us} UL943 C22.2 No. 144	cUL _{us} UL498 C22.2 No. 42	FSUL WC596
Specification Grade 15 Amp Duplex GFCI							
PT1595I	15	125	Ivory	5-15R	•	•	•
PT1595W	15	125	White	5-15R	•	•	•
PT1595	15	125	Brown	5-15R	•	•	•
PT1595GRY	15	125	Gray	5-15R	•	•	•
PT1595BK	15	125	Black	5-15R	•	•	•
PT1595RED	15	125	Red	5-15R	•	•	•
PT1595LA	15	125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI							
PT2095I	20	125	Ivory	5-20R	•	•	•
PT2095W	20	125	White	5-20R	•	•	•
PT2095	20	125	Brown	5-20R	•	•	•
PT2095GRY	20	125	Gray	5-20R	•	•	•
PT2095BK	20	125	Black	5-20R	•	•	•
PT2095RED	20	125	Red	5-20R	•	•	•
PT2095LA	20	125	Light Almond	5-20R	•	•	•

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

For additional PlugTail Connectors, see Page B-3.

All PlugTail Connectors are available in any wire length up to 25 inches, consult factory to order.



PTRA6STR

All devices listed on this page conform to NEMA WD-1 and WD-6.


PlugTail™ Spec Grade GFCIs



Pass & Seymour

GFCIs PlugTail™ Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



PT2095HGW




Features

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications



- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI							
PT1595HGI	15	125	Ivory	5-15R	•	•	•
PT1595HGW	15	125	White	5-15R	•	•	•
PT1595HG	15	125	Brown	5-15R	•	•	•
PT1595HGGRY	15	125	Gray	5-15R	•	•	•
PT1595HGRED	15	125	Red	5-15R	•	•	•
PT1595HGLA	15	125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI							
PT2095HGI	20	125	Ivory	5-20R	•	•	•
PT2095HGW	20	125	White	5-20R	•	•	•
PT2095HG	20	125	Brown	5-20R	•	•	•
PT2095HGGRY	20	125	Gray	5-20R	•	•	•
PT2095HGRED	20	125	Red	5-20R	•	•	•
PT2095HGLA	20	125	Light Almond	5-20R	•	•	•



PTR6STR

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



For additional PlugTail Connectors, see Page B-3.

All PlugTail Connectors are available in any wire length up to 25 inches, consult factory to order.

GFCIs


PlugTail™ Specification & Hospital Grade Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




GFCIs


Features	
<ul style="list-style-type: none"> ■ Protects children: patented shutter system helps prevent improper insertion of foreign objects. ■ Meets National Electrical Code® Tamper-Resistant requirements. ■ Faster, more reliable installation. ■ No exposed terminals create a finger safe application before, during, and after installation. ■ Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector. ■ GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. 	<ul style="list-style-type: none"> ■ FSUL Listed (Federal Specification WC596). ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ Trip indicator light (red LED). ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Zinc-plated steel mounting strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.




PT2095TRW



PT2095HGTRW



PTR6A6STR



Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Specification Grade Tamper-Resistant 15 Amp Duplex GFCI							
PT1595TRI	15	125	Ivory	5-15R	•	•	•
PT1595TRW	15	125	White	5-15R	•	•	•
PT1595TR	15	125	Brown	5-15R	•	•	•
PT1595TRGRY	15	125	Gray	5-15R	•	•	•
PT1595TRBK	15	125	Black	5-15R	•	•	•
PT1595TRRED	15	125	Red	5-15R	•	•	•
PT1595TRLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI							
PT2095TRI	20	125	Ivory	5-20R	•	•	•
PT2095TRW	20	125	White	5-20R	•	•	•
PT2095TR	20	125	Brown	5-20R	•	•	•
PT2095TRGRY	20	125	Gray	5-20R	•	•	•
PT2095TRBK	20	125	Black	5-20R	•	•	•
PT2095TRRED	20	125	Red	5-20R	•	•	•
PT2095TRLA	20	125	Light Almond	5-20R	•	•	•
Hospital Grade Tamper-Resistant 15 Amp Duplex GFCI							
PT1595HGTRI	15	125	Ivory	5-15R	•	•	•
PT1595HGTRW	15	125	White	5-15R	•	•	•
PT1595HGTRGRY	15	125	Gray	5-15R	•	•	•
PT1595HGTRRED	15	125	Red	5-15R	•	•	•
PT1595HGTRLA	15	125	Light Almond	5-15R	•	•	•
Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI							
PT2095HGTRI	20	125	Ivory	5-20R	•	•	•
PT2095HGTRW	20	125	White	5-20R	•	•	•
PT2095HGTRGRY	20	125	Gray	5-20R	•	•	•
PT2095HGTRRED	20	125	Red	5-20R	•	•	•
PT2095HGTRLA	20	125	Light Almond	5-20R	•	•	•

For PlugTail Connector catalog numbers, see Page C-13 or C-14.

All devices listed on this page conform to NEMA WD-1 and WD-6.


PlugTail™ Tamper-Resistant GFCIs




Pass & Seymour

GFCIs PlugTail™ Specification & Hospital Grade Tamper-Resistant Nightlight/GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



PT1595NTLTRI



PT1595HGNTLTRI



PTRA6STR

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
NEW Specification Grade Tamper-Resistant 15 Amp Combination Nightlight/GFCI							
PT1595NTLTRI	15	125	Ivory	5-15R	•	•	•
NEW Specification Grade Tamper-Resistant 20 Amp Combination Nightlight/GFCI							
PT2095NTLTRI	20	125	Ivory	5-20R	•	•	•
PT2095NTLTRW	20	125	White	5-20R	•	•	•
NEW Hospital Grade Tamper-Resistant 15 Amp Combination Nightlight/GFCI							
PT1595HGNTLTRI	15	125	Ivory	5-15R	•	•	•
PT1595HGNTLTRW	15	125	White	5-15R	•	•	•
PT1595HGNTLRRD	15	125	Red	5-15R	•	•	•
NEW Hospital Grade Tamper-Resistant 20 Amp Combination Nightlight/GFCI							
PT2095HGNTLTRI	20	125	Ivory	5-20R	•	•	•
PT2095HGNTLTRW	20	125	White	5-20R	•	•	•
PT2095HGNTLTRLA	20	125	Light Almond	5-20R	•	•	•



NEMA 5-15R



NEMA 5-20R

For PlugTail Connector catalog numbers, see Page C-13 or C-14.

GFCIs NAFTA-Compliant & RoHS-Compliant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

GFCIs

NEW


Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	FSUL WC596
NAFTA-Compliant TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI							
1595TRNAI	15	125	Ivory	5-15R	•	•	•
1595TRNAW	15	125	White	5-15R	•	•	•
1595TRNA	15	125	Brown	5-15R	•	•	•
1595TRNAGRY	15	125	Gray	5-15R	•	•	•
1595TRNABK	15	125	Black	5-15R	•	•	•
1595TRNALA	15	125	Light Almond	5-15R	•	•	•



2095TRNAW

NEW

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	FSUL WC596
NAFTA-Compliant TradeMaster®/Spec Grade Tamper-Resistant 20 Amp Duplex GFCI							
2095TRNAI	20	125	Ivory	5-20R	•	•	•
2095TRNAW	20	125	White	5-20R	•	•	•
2095TRNA	20	125	Brown	5-20R	•	•	•
2095TRNAGRY	20	125	Gray	5-20R	•	•	•
2095TRNABK	20	125	Black	5-20R	•	•	•
2095TRNALA	20	125	Light Almond	5-20R	•	•	•



1595NAW

NEW

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	FSUL WC596
NAFTA-Compliant TradeMaster®/Spec Grade 15 Amp Duplex GFCI							
1595NAI	15	125	Ivory	5-15R	•	•	•
1595NAW	15	125	White	5-15R	•	•	•
1595NA	15	125	Brown	5-15R	•	•	•
1595NAGRY	15	125	Gray	5-15R	•	•	•
1595NABK	15	125	Black	5-15R	•	•	•
1595NALA	15	125	Light Almond	5-15R	•	•	•

NEW


Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	FSUL WC596
NAFTA-Compliant Spec Grade 20 Amp Duplex GFCI							
2095NAI	20	125	Ivory	5-20R	•	•	•
2095NAW	20	125	White	5-20R	•	•	•
2095NA	20	125	Brown	5-20R	•	•	•
2095NAGRY	20	125	Gray	5-20R	•	•	•
2095NABK	20	125	Black	5-20R	•	•	•
2095NALA	20	125	Light Almond	5-20R	•	•	•



NAFTA-Compliant GFCI Receptacles are ideal for use on projects subject to the provisions of the Buy American Act.

NEW

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	FSUL WC596
RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI							
1595RI	15	125	Ivory	5-15R	•	•	•
1595RW	15	125	White	5-15R	•	•	•
1595RLA	15	125	Light Almond	5-15R	•	•	•



1595RW

RoHS-Compliant GFCI Receptacles meet the requirements of Restriction of Hazardous Substances directives and regulations.



NEMA 5-15R



NEMA 5-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.


NAFTA-Compliant & RoHS-Compliant GFCIs




Pass & Seymour

GFCIs NAFTA-Compliant Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



2095HGTRNAW





1595HGNAW

NEW

NEW

NEW

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	VAC			UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI							
2095HGTRNAI	20	125	Ivory	5-20R	•	•	•
2095HGTRNAW	20	125	White	5-20R	•	•	•
2095HGTRNAGRY	20	125	Gray	5-20R	•	•	•
2095HGTRNARED	20	125	Red	5-20R	•	•	•
2095HGTRNALA	20	125	Light Almond	5-20R	•	•	•
NAFTA-Compliant Hospital Grade 15 Amp Duplex GFCI							
1595HGNAI	15	125	Ivory	5-15R	•	•	•
1595HGNAW	15	125	White	5-15R	•	•	•
1595HGNA RED	15	125	Red	5-15R	•	•	•
NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI							
2095HGNAI	20	125	Ivory	5-20R	•	•	•
2095HGNAW	20	125	White	5-20R	•	•	•
2095HGNA	20	125	Brown	5-20R	•	•	•
2095HGNA GRY	20	125	Gray	5-20R	•	•	•
2095HGNA RED	20	125	Red	5-20R	•	•	•
2095HGNALA	20	125	Light Almond	5-20R	•	•	•



NAFTA-Compliant GFCI Receptacles are ideal for use on projects subject to the provisions of the Buy American Act.

All devices listed on this page conform to NEMA WD-1 and WD-6.

GFCIs NAFTA-Compliant PlugTail™ GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC




Pass & Seymour

GFCIs


Features	
<ul style="list-style-type: none"> ■ Faster, more reliable installation. ■ No exposed terminals create a finger safe application before, during, and after installation. ■ Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector. ■ GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings. ■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. ■ FSUL Listed (Federal Specification WC596). 	<ul style="list-style-type: none"> ■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. ■ Trip indicator light (red LED). ■ Mounting screws are shipped captive in the device and wall plate for easier installation. ■ High-impact-resistant thermoplastic construction. ■ Zinc-plated steel mounting strap. ■ Button colors match the device face. ■ Dual-direction test and reset buttons. ■ Class A rated GFCI. ■ Supplied with matching TP26 nylon wall plate. ■ Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132 VAC ■ Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> ■ Trip Time: 0.025 sec., nominal per UL Standard ■ 20 Amp feed-thru capacity




PT1595NAW



PT2095TRNAW



PT2095NTLTRNAW



Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL _{us} UL943 C22.2 No. 144	cUL _{us} UL498 C22.2 No. 42	FSUL WC596
NEW NAFTA-Compliant Spec Grade 15 Amp Duplex GFCI							
PT1595NAI	15	125	Ivory	5-15R	•	•	•
PT1595NAW	15	125	White	5-15R	•	•	•
PT1595NAGRY	15	125	Gray	5-15R	•	•	•
PT1595NALA	15	125	Light Almond	5-15R	•	•	•
NEW NAFTA-Compliant Spec Grade 20 Amp Duplex GFCI							
PT2095NAI	20	125	Ivory	5-20R	•	•	•
PT2095NAW	20	125	White	5-20R	•	•	•
PT2095NAGRY	20	125	Gray	5-20R	•	•	•
PT2095NABK	20	125	Black	5-20R	•	•	•
PT2095NALA	20	125	Light Almond	5-20R	•	•	•
NEW NAFTA-Compliant Spec Grade Tamper-Resistant 20 Amp Duplex GFCI							
PT2095TRNAI	20	125	Ivory	5-20R	•	•	•
PT2095TRNAW	20	125	White	5-20R	•	•	•
PT2095TRNAGRY	20	125	Gray	5-20R	•	•	•
PT2095TRNALA	20	125	Light Almond	5-20R	•	•	•
NEW NAFTA-Compliant Spec Grade Tamper-Resistant 15 Amp Combination Nightlight/GFCI							
PT1595NTLTRNAI	15	125	Ivory	5-15R	•	•	•
PT1595NTLTRNAW	15	125	White	5-15R	•	•	•
NEW NAFTA-Compliant Spec Grade Tamper-Resistant 20 Amp Combination Nightlight/GFCI							
PT2095NTLTRNAI	20	125	Ivory	5-20R	•	•	•
PT2095NTLTRNAW	20	125	White	5-20R	•	•	•

NAFTA-Compliant GFCI Receptacles are ideal for use on projects subject to the provisions of the Buy American Act.

For PlugTail Connector catalog numbers, see Page C-20.

All devices listed on this page conform to NEMA WD-1 and WD-6.


NAFTA-Compliant PlugTail™ GFCI Receptacles




Pass & Seymour

GFCIs NAFTA-Compliant PlugTail™ Hospital Grade GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



PT2095HGNAW



PT2095HGNTLTRNAW



PTR6STR



NEMA 5-15R



NEMA 5-20R

Features

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- Trip Threshold: 5± 1mA
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
NEW NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI							
PT2095HGNAI	20	125	Ivory	5-20R	•	•	•
PT2095HGNAW	20	125	White	5-20R	•	•	•
PT2095HGNAWGRY	20	125	Gray	5-20R	•	•	•
PT2095HGNAWRED	20	125	Red	5-20R	•	•	•
PT2095HGNAWALA	20	125	Light Almond	5-20R	•	•	•
NEW NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI							
PT2095HGTRNAI	20	125	Ivory	5-20R	•	•	•
PT2095HGTRNAW	20	125	White	5-20R	•	•	•
PT2095HGTRNAWGRY	20	125	Gray	5-20R	•	•	•
PT2095HGTRNAWRED	20	125	Red	5-20R	•	•	•
PT2095HGTRNAWALA	20	125	Light Almond	5-20R	•	•	•
NEW NAFTA-Compliant Hospital Grade Tamper-Resistant 15 Amp Combination Nightlight/GFCI							
PT1595HGNTLTRNAI	15	125	Ivory	5-15R	•	•	•
PT1595HGNTLTRNAW	15	125	White	5-15R	•	•	•
PT1595HGNTLTRNAWRED	15	125	Red	5-15R	•	•	•
NEW NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Combination Nightlight/GFCI							
PT2095HGNTLTRNAI	20	125	Ivory	5-20R	•	•	•
PT2095HGNTLTRNAW	20	125	White	5-20R	•	•	•
PT2095HGNTLTRNAWRED	20	125	Red	5-20R	•	•	•

NAFTA-Compliant GFCI Receptacles are ideal for use on projects subject to the provisions of the Buy American Act.

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTR6STR	Stranded	6"
PTR6SOL	Solid	6"

For additional PlugTail Connectors, see Page B-3.

All PlugTail Connectors are available in any wire length up to 25 inches, consult factory to order.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Applications
All Legrand/Pass & Seymour Portable GFCIs meet OSHA and NEC requirements to provide ground fault protection for personnel utilizing temporary power during construction, remodeling, maintenance, repair and demolition. Can be used with power tools, high-pressure power washers, wet vacuums, and grounds keeping equipment. Also used on spas, hot tubs, vending machines, and portable signs to provide ground fault protection.

Open Neutral Protection
All Legrand/Pass & Seymour portable GFCIs have an open neutral relay that automatically cuts off power to the line (hot) conductor of the device in the event that the neutral wire preceding the GFCI becomes severed. For example, if your portable GFCI were plugged into an extension cord that was supplying the power and the neutral conductor on that extension cord was accidentally cut (as can happen on a job site), the open neutral relay would shut off power to the hot conductor. This provides an additional level of safety from possible ground faults.

Manual Reset GFCI
Requires the GFCI to be manually set for use by pressing the reset button upon plug in and after loss of primary power (power failure or unplugging the device). Must be manually reset after a ground fault condition. Ideal for applications where operator injury might occur if equipment were to restart after a power failure. Typical equipment includes power drills, saws, lathes, and grinders.

Automatic Reset GFCI
Automatically energizes or sets the GFCI for use upon plug in and after the loss of primary power (power failure or unplugging the device). After a ground fault condition, must be reset by pushing the reset button. This feature eliminates the need for unit to be reset each time it is plugged in or powered up. Ideal for equipment intended for continuous use where a temporary power failure is likely and undesirable. Examples are pumps, pressure washers, portable signs, or lighting and engine heaters.

- Features & Specifications**
- Durable polycarbonate case withstands hard use.
 - Open neutral protection.
 - Supply Voltage: 125VAC, 60 Hz
 - Supply Voltage Range: 102-132VAC
 - Operating Temperature: -35°C (-30°F) to +66°C (150°F)
 - Trip Time: .025 sec., nominal per UL Standard
 - Trip Threshold: 5±1mA
 - Cord Grip Range: .30"-.46"
 - RoHS-Compliant.



1594CMM


Catalog Number	Reset	Rating A. VAC	NEMA Config. No.	GFCI	Right Angle Plug	3rd Party Compliance		
						UL943	UL498	C22.2 No. 144
Right Angle Plug – Portable GFCI								
1594CMM	Manual	15 125	5-15P		User attachable	•	•	•
1594CMA	Automatic	15 125	5-15P		User attachable	•	•	•

RoHS-Compliant Portable GFCIs meet the requirements of Restriction of Hazardous Substances directives and regulations.




Pass & Seymour


GFCIs Portables




1594PC2A



1594TC2A



2094TL2M



2094PC2A

Features & Specifications	
<ul style="list-style-type: none"> ■ Durable polycarbonate case withstands hard use. ■ In-line has power indicator light that is on when power is available. ■ Open neutral protection. ■ Optional Turnlok® plugs and connectors prevent accidental disconnection. ■ Optional tri-cord connector handles up to three loads. 	<ul style="list-style-type: none"> ■ Supply Voltage: 125VAC, 60 Hz ■ Supply Voltage Range: 102-132VAC ■ Operating Temperature: -35°C (-30°F) to +66°C (150°F) ■ Trip Time: .025 sec., nominal per UL Standard ■ Trip Threshold: 5±1mA ■ RoHS-Compliant.

Catalog Number	Description	Reset	Rating A. VAC	NEMA Config. No.	Plug	Conn.	3rd Party Compliance		
							UL943	UL498	C22.2 No. 144
15 Amp In-Line – Portable GFCI									
1594PC6M	6' cord, straight blade	Manual	15 125	5-15P/R			•	•	•
1594PC2M	2' cord, straight blade	Manual	15 125	5-15P/R			•	•	•
1594PC2A	2' cord, straight blade	Auto.	15 125	5-15P/R			•	•	•
1594TC2M	2' cord with tri-cord connector	Manual	15 125	5-15P/R			•	•	•
1594TC2A	2' cord with tri-cord connector	Auto.	15 125	5-15P/R			•	•	•
20 Amp In-Line Portable GFCI									
2094PC2A	2' cord, straight blade	Auto.	20 125	5-20P/R			•	•	•
2094PC2M	2' cord, straight blade	Manual	20 125	5-20P/R			•	•	•
2094TL2A	2' cord, Turnlok®	Auto.	20 125	L5-20P/R			•	•	•
2094TL2M	2' cord, Turnlok®	Manual	20 125	L5-20P/R			•	•	•

Catalog Number	Description	Reset	Rating A. VAC	NEMA Config. No.	Plug	Conn.	3rd Party Compliance		
							UL943	UL498	C22.2 No. 144
Cord Set – Portable GFCI									
1594CS1M	1' cord with connector	Manual	15 125	5-15P/R			•	•	•
1594CS1A	1' cord with connector	Automatic	15 125	5-15P/R			•	•	•










1594CS1M
1594CS1A

RoHS-Compliant Portable GFCIs meet the requirements of Restriction of Hazardous Substances directives and regulations.

Features & Specifications

- Handles up to four loads.
- Open neutral protection.
- High-impact-resistant thermoplastic housing.
- Optional Turnlok[®] plugs and connectors prevent accidental disconnection.
- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Threshold: 5±1mA
- Trip Time: .025 sec., nominal per UL Standard
- Case Material: Yellow Thermoplastic



Catalog Number	Description	Rating A. VAC	NEMA Config. No.	Plug	Receptacle	3rd Party Compliance	
						UL	UL
Auto Reset Boxes – Portable GFCI							
PS154S	Four 15A, 125V straight blade outlets. Cord has 15A, 125V plug	15 125	5-15P 5-15R			•	•
PS204S	Four 20A, 125V straight blade outlets. Cord has 20A, 125V plug	20 125	5-20P 5-20R			•	•
PL204L	Two 20A, 125V straight blade outlets and one 20A 125V locking outlet has 20A, 125V locking plug	20 125	L5-20P L5-20R 5-20R			•	•