



**CREE**  **LIGHTING**



## INDOOR LED PRODUCTS

---

DYNAMIC LIGHTING EXPERIENCE	2
SPECIFICATION LINEAR	4
SPECIFICATION DOWNLIGHT	6
RETROFIT DOWNLIGHTS	8
TROFFERS	10
UPGRADE SOLUTIONS	14
SUSPENDED AMBIENT	18
SURFACE AMBIENT	22
HIGH-BAY/LOW-BAY	26
LAMPS	30
TRACK LIGHTING	34
TRACK ACCESSORIES	40

## OUTDOOR LED PRODUCTS

---

AREA	44
DECORATIVE STREET & ROADWAY	48
STREET & ROADWAY	52
CANOPY & SOFFIT	56
PARKING STRUCTURE	60
FLOOD	64
WALL MOUNT	68

## CREE LIGHTING TECHNOLOGIES

---

SMARTCAST INTELLIGENCE PLATFORM™	71
WAVEMAX® TECHNOLOGY	76
COLORFAST DELTAGUARD® FINISH	76
CREE TRUEWHITE® TECHNOLOGY	77
NANOOPTIC® TECHNOLOGY	77

\*LED lighting replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.

# LED DYNAMIC LIGHTING EXPERIENCE







## Cadant™ Dynamic Lighting Experience



- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• CCT: 3000K - 6500K</li> <li>• Up to 3200 lumens</li> <li>• Up to 75 LPW</li> <li>• 5" regressed housing</li> <li>• Smartcast® Technology to 5% with east to west sun feature</li> </ul> | <ul style="list-style-type: none"> <li>• CRI &gt;90, R<sub>9</sub> &gt;65</li> <li>• TM30 Color: Fidelity (R<sub>f</sub>) &gt; 90, Gamut (R<sub>g</sub>) &gt;100</li> <li>• Assembled in the U.S.A of U.S. and imported parts</li> </ul> |
|--|--|

**APPLICATIONS:** Office, education, healthcare, retail, hospitality


- Independently controlled, separate sun and sky panels create unique east to west sun feature
- Recreates the dynamic experience of being under the natural sky
- Valuable sensory connection to the outdoors for people without access to windows
- Enhances architectural designs with visual impact and dramatic scene setting
- Supports wellness, productivity and the natural rhythms of the day
- Fully-illuminated panels provide omnidirectional light distribution similar to actual daylight
- Advanced lighting control and color changing capabilities while interacting with and connecting to other fixtures in the space to create an overall scene that fits the needs of the space
- An intuitive, wall-mounted touchscreen with a clean graphic interface gives fingertip control over multiple Cadant™ luminaires
- Dawn, Morning, Midday, Afternoon, and Evening presets are standard; end users can easily create and save their own presets customizing light levels and color (CCT)
- Preloaded profiles are included – Hospital, Office, School & Follow-the-Sun – with the ability to change sky color, CCT & sun position
- Measures very high for R<sub>f</sub> Skin, showing people in the best light and aiding in accurate diagnoses in healthcare spaces

# LED SPECIFICATION LINEAR







### MOUNTING OPTIONS / OPTICS




Linear  
Recessed\*




Linear  
Suspended  
Direct\*




Linear  
Suspended  
Direct/Indirect\*




Linear  
Surface Mount\*



Linear Wall  
Direct



Linear Wall  
Direct/  
Indirect



Linear Wall  
Wash/Asymmetric  
Optic

## Stylus™ Linear Series

Specification-grade modern 3" linear portfolio designed around architectural simplicity and human comfort

- Horizontal corners for geometric patterning and shape creation
- Full linear 3" portfolio to design an entire space: suspended, recessed, surface and wall mounts
- Uplight/downlight option for both suspended and wall mount
- Downlight Optics: Lambertian and Wall Wash
- Continuous row options from 2' to 72' (120V) or 144' (277V) with just one power drop for easy installation
- Three housing color options of white, black and graphite
- 80 CRI (For DLC Certifications)
- 90+ CRI, R9>65
- TM30 Color: Fidelity ( $R_f$ ) > 92, Gamut ( $R_g$ ) >100
- CCT: 3000K, 3500K, 4000K
- 90 CRI: 400 lumens/ft (low), 650 lumens/ft (medium), 900 lumens/ft (high)
- 80 CRI: 500 lumens/ft (low), 800 lumens/ft (medium), 1100 lumens/ft (high)
- 80 CRI: Up to 110 LPW, 90 CRI: Up to 90 LPW
- 120-277 VAC or 347 VAC
- 10-year limited warranty
- Individual mount or continuous row for recess, surface, suspended and wall mount
- 0-10V dimming to 1%, Smartcast, Lutron EcoSystem and Lutron Vive, DALI dimming to 5%
- Made in the U.S.A of U.S. and imported parts

**APPLICATIONS:** Office, education, healthcare, retail, hospitality



\* Also available in asymmetric

# LED SPECIFICATION DOWNLIGHTS



Cree® LED specification downlights allow designers to meet interior lighting performance requirements while achieving beautiful color consistency with easy installation.



KR8™



KR6™ Square



KR6™ Round

## KR Series

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• Minimum 90 CRI</li> <li>• CCT: 2700K, 3000K, 3500K, 4000K, 5000K</li> <li>• Up to 8000 lumens</li> <li>• Input Power: 13W – 118W</li> <li>• Cree TrueWhite® Technology</li> <li>• Cree WaveMax® Technology in 8" round for precise optical control</li> <li>• Controls/Dimming: KR4 and KR6: TRIAC 5%, 0-10V 10%, KR8: 0-10V 1%, Cree Sunset Dimming Technology [2700K – 1800K CCT], SmartCast® Technology to 5%, and Lutron EcoSystem® Enabled to 5%</li> </ul> | <ul style="list-style-type: none"> <li>• 4" or 6" round and square apertures with Sunset Dimming from 2700K to 1800K, and SmartCast® Technology</li> <li>• 10-year limited warranty</li> <li>• Made in the U.S.A of U.S. and imported parts</li> </ul> |
|---|--|

**APPLICATIONS:** New construction (heights up to 40')



6" Downlight



4" Downlight



Adjustable Downlight

## Essentia® Series Downlights

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• 90+ CRI</li> <li>• CCT: 2700K, 3000K, 3500K, 4000K</li> <li>• Up to 6315 lumens</li> <li>• Input Power: 12W – 86W</li> <li>• 0-10V continuous dimming to 1%, TRIAC dimming to 10%</li> </ul> | <ul style="list-style-type: none"> <li>• 4", 6" and 8" round apertures, along with wall wash and adjustable accent configurations</li> <li>• Available with Emergency Backup option</li> <li>• 5-year limited warranty</li> </ul> |
|---|---|

**APPLICATIONS:** New construction and retrofit



# LED RETROFIT DOWNLIGHTS





Cree® LED retrofit downlights deliver beautiful light with superior color quality and high energy efficiency — a true no-compromise solution that takes only seconds to install.



## LRX Series

**Replaces multi-CFL pin-based configurations up to 42 watts.**

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• 90 CRI</li> <li>• R9: &gt;54</li> <li>• CCT: 2700K, 3500K, 4000K</li> <li>• 650 - 3,000 lumens</li> <li>• Up to 100 LPW</li> <li>• Input Power: 7.5W - 34W</li> </ul> | <ul style="list-style-type: none"> <li>• Cree TrueWhite® Technology</li> <li>• Continuous dimming to 5%</li> <li>• Deep recess for reduced glare</li> <li>• 10-year limited warranty</li> </ul> |
|--|---|

**APPLICATIONS:** Recessed lighting in both new construction and retrofit commercial settings



## CR-T Series

**Replaces 75W, 100W or 150W incandescent downlights.**

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• 90 CRI</li> <li>• CCT: 2700K, 3000K, 3500K, 4000K</li> <li>• Up to 1650 lumens</li> <li>• Input Power: 10.5W - 21W</li> <li>• NEW: Universal and Gimbal options available</li> </ul> | <ul style="list-style-type: none"> <li>• Deep recess options for reduced glare</li> <li>• Dimmable with TRIAC dimmers at 120V</li> <li>• 4" and 6" sizes</li> <li>• 5-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Recessed lighting in both new and retrofit residential and light commercial



## DDS Series

**Replaces 65W or 75W incandescent downlights.**

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• 90 CRI</li> <li>• CCT: 2700K, 3000K, 4000K</li> <li>• 750 or 900 lumens</li> <li>• Up to 85 LPW</li> <li>• Input Power: 9W or 10.5W</li> </ul> | <ul style="list-style-type: none"> <li>• 4" and 6" sizes</li> <li>• Dimmable with most standard dimmers</li> <li>• Wet rated</li> <li>• 5-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Recessed lighting in both new and retrofit residential and light commercial



# LED TROFFERS





## CR Series

**Replaces linear fluorescent fixtures in new construction or renovation.**

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• 80+ – 90 CRI</li> <li>• CCT: 3000K, 3500K, 4000K, 5000K or adjustable CCT with Cree SmartCast® Technology</li> <li>• 2000 to 5000 lumens</li> <li>• 90 - 130 LPW</li> <li>• Input Power: 22W – 50W</li> </ul> | <ul style="list-style-type: none"> <li>• Cree TrueWhite® Technology (90 CRI)</li> <li>• Available with Cree SmartCast® Technology; step level to 50%, 0-10V dimming to 5% or Lutron EcoSystem® Enabled to 5%</li> <li>• 10-year limited warranty</li> </ul> |
|--|---|



SmartCast® Technology optional



Adjustable CCT with optional SmartCast® Technology

**APPLICATIONS: Office, education and healthcare**



On CR HD and CR TW



On CR HE TW



## ZR Series

**Replaces linear fluorescent fixtures in new construction or renovation.**

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• 80+ CRI for ZR-FD &amp; ZR-C</li> <li>• 90+ CRI for ZR-MT &amp; ZR Series</li> <li>• CCT: 3000K, 3500K, 4000K or 5000K*</li> <li>• 2000 to 10,000 lumens</li> <li>• High efficacy up to 135 LPW</li> <li>• Input Power: 15W – 74W</li> <li>• Cree TrueWhite® Technology (90 CRI)</li> </ul> | <ul style="list-style-type: none"> <li>• 0-10V, Smartcast Wireless, DALI, Lutron Vive, Lutron EcoSystem</li> <li>• Intuitive removable lens</li> <li>• 10-year limited warranty for ZR-FD, ZR-MT and ZR Series</li> <li>• 5-year limited warranty on ZR-C Series</li> </ul> |
|--|---|



Removable lens

**APPLICATIONS: Office, education and healthcare**



On ZRMT TW



On ZRM-FD and ZRC-FD

\* Not available on all types



## FLEX Series

**Specification LED troffer that replaces linear fluorescent fixtures in new construction or renovation.**

- 83+ CRI
- CCT: 3000K, 3500K, 4000K, 5000K
- 3200 or 5000 lumens (2x2)
- 3200, 4000, 5000 or 6000 lumen options (2x4, 1x4)
- Up to 145 LPW
- Input Power: 23W - 43W
- 0-10V dimming to 1% standard; SmartCast® Technology optional
- Inner Optic accessory options for more flexibility and enhanced aesthetics
- Brushed Metal, Striped, Perforated, Wavy, and Standard Diffused options
- Emergency Battery option on board
- 10-year limited warranty

**APPLICATIONS: Office, retail, education, and healthcare**

Targeted to meet DLC Premium certification



### 5 INNER OPTIC DESIGN CHOICES

The inner optics simply snap into the FLEX lens channel for enhanced design flexibility.



*Brushed Metal*



*Striped*




*Perforated*



*Wavy*



*Standard Diffused*





Green Team (301-311)  
Nurse Station



Red Team (401-410)  
Nurse Station



# LED UPGRADE SOLUTIONS





Cree® LED upgrade solutions offer customers the ability to maintain the existing aesthetic of a fluorescent fixture but take advantage of the greater energy efficiency and long lifespan of LED lights.



COMING SOON

## ZR-RK Commercial Series LED Troffer Retrofit Kit

**PRELIMINARY**

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>• 80+ CRI</li><li>• CCT: 3000K, 3500K, 4000K, 5000K</li><li>• 2600 - 7000 lumens</li><li>• Up to 130 LPW</li></ul> | <ul style="list-style-type: none"><li>• Input Power: 20W - 54W</li><li>• 0-10V, Smartcast Wireless, DALI, Lutron Vive, Lutron EcoSystem</li><li>• 5-year limited warranty</li></ul> |
|--|---|

**APPLICATIONS:** Office, education, hospitality, healthcare and petroleum.




UR2-24  
2' Lightbar  
UpgradeKit



UR2-48  
4' Lightbar  
Upgrade Kit



UR3-24  
2' Lightbar  
Upgrade Kit



UR3-48  
4' Lightbar  
Upgrade Kit



COMING SOON

# UR Series LED Upgrade Kit

Replaces existing fluorescent troffers and linear fluorescent fixtures.

## PRELIMINARY

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>• 80 CRI</li><li>• CCT: 3000K, 3500K, 4000K, 5000K</li><li>• 1300 or 1600 lumens for 2' lightbar</li><li>• 2100 or 2500 lumens for 4' lightbar</li><li>• Up to 155 LPW</li></ul> | <ul style="list-style-type: none"><li>• Input Power: 9W-17.5W</li><li>• 0-10V dimming; step dimming available soon</li><li>• Available in 2-, 3- or 4-lamp options</li><li>• 120-277V</li><li>• 5-year limited warranty</li></ul> |
|--|---|

APPLICATIONS: Office, education, hospitality, healthcare and petroleum



# LED SUSPENDED AMBIENT



Cree’s suspended ambient indirect/direct luminaire gives architects an adaptable and supremely high-functioning light system with a super-modern, low-profile look at an appealing price point.



Square Beauty  
End Cap

# LSQ Square Series

Replaces linear fluorescent lamp systems, strips, wraps and more.


<ul style="list-style-type: none"><li>• 80+, 90 CRI</li><li>• CCT: 3500K, 4000K, 5000K</li><li>• 4,000 - 10,000 lumens</li><li>• Up to 130 LPW</li><li>• Input Power: 44W - 87W</li><li>• 120-277 or 347 VAC</li></ul>	<ul style="list-style-type: none"><li>• 0-10V dimming to 5%</li><li>• Individual mount or continuous row - surface mount, suspended, pendant and cove</li><li>• 5-year limited warranty LSQ-C; 10-year limited warranty LSQ</li></ul>
--	---

APPLICATIONS: Office, education, grocery and retail





Round beauty end caps available



Suspended mount with optional reflectors

# LS Series

Replaces linear fluorescent lamp systems, strips, wraps and more.

- |   |  |
|---|--|
| <ul style="list-style-type: none"><li>• 90+ CRI (LS TrueWhite®) or 80+ CRI (LS-C)</li><li>• CCT: 3500K, 4000K, 5000K</li><li>• 2500, 4000 and 5000 lumens for 4'</li><li>• 8000 and 10,000 lumens for 8'</li><li>• Up to 150 LPW</li><li>• Input Power: 44W and 88W (LS TrueWhite®) 20W and 51W (LS-C)</li><li>• Cree TrueWhite® Technology</li></ul> | <ul style="list-style-type: none"><li>• 0-10V dimming to 5%</li><li>• 4' and 8' sizes</li><li>• Occupancy Sensor accessory and thru-wiring option available (S-WRAC-OC-1)</li><li>• 10-year limited warranty for LS TrueWhite®</li><li>• 5-year limited warranty on LS-C</li></ul> |
|---|--|

APPLICATIONS: Industrial, manufacturing, grocery and retail



LS TrueWhite®



LS-C





# LED SURFACE AMBIENT






Cree® surface ambient fixtures provide exceptional illumination performance, cost-effective lighting and are designed for easy installation to save time and money.



Round beauty end caps available



Suspended mount with optional reflectors

## LS Series

**Replaces linear fluorescent lamp systems, strips, wraps and more.**

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• 90+ CRI (LS TrueWhite®) or 80+ CRI (LS-C)</li> <li>• CCT: 3500K, 4000K, 5000K</li> <li>• 2500, 4000 and 5000 lumens for 4'</li> <li>• 8000 and 10,000 lumens for 8'</li> <li>• Up to 150 LPW</li> <li>• Input Power: 44W and 88W (LS TrueWhite®) 20W and 51W (LS-C)</li> <li>• Cree TrueWhite® Technology</li> </ul> | <ul style="list-style-type: none"> <li>• 0-10V dimming to 5%</li> <li>• 4' and 8' sizes</li> <li>• Occupancy Sensor accessory and thru-wiring option available (S-WRAC-OC-1)</li> <li>• 10-year limited warranty for LS TrueWhite®</li> <li>• 5-year limited warranty on LS-C</li> </ul> |
|---|--|

**APPLICATIONS: Industrial, manufacturing, grocery and retail**



LS TrueWhite®




LS-C

## LSQ Square Series

**Replaces linear fluorescent lamp systems, strips, wraps and more.**

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• 80+, 90 CRI</li> <li>• CCT: 3500K, 4000K, 5000K</li> <li>• 4,000 - 10,000 lumens</li> <li>• Up to 130 LPW</li> <li>• Input Power: 44W - 87W</li> <li>• 120-277 or 347 VAC</li> </ul> | <ul style="list-style-type: none"> <li>• 0-10V dimming to 5%</li> <li>• Individual mount or continuous row - surface mount, suspended, pendant and cove</li> <li>• 5-year limited warranty LSQ-C; 10-year limited warranty LSQ</li> </ul> |
|---|---|

**APPLICATIONS: Office, education, grocery and retail**



Square Beauty End Cap



## WS Series

**Replaces linear fluorescent lamp systems, strips, wraps and more.**

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• 80 CRI</li><li>• CCT: 3500K, 4000K, 5000K</li><li>• 4100 or 6100 lumens</li><li>• Up to 142 LPW</li><li>• Input Power: 30W - 43W</li></ul> | <ul style="list-style-type: none"><li>• 0-10V dimming to 10% (standard)</li><li>• IP65 and IP66 rated</li><li>• NSF Splash Zone II certified</li><li>• 5-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Industrial, manufacturing, grocery and retail settings





# LED HIGH-BAY/LOW-BAY



Cree® interior high-bay and low-bay lighting is the ideal source for energy-efficient, low-maintenance illumination in large spaces.



## KBL Series

Replaces 250W, 400W HID or up to six-lamp 54W T5HO fixtures.

- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• 70, 80+ CRI</li> <li>• CCT: 3000K, 3500K, 4000K, 5000K</li> <li>• 9,000 - 30,000 lumens</li> <li>• Up to 156 LPW</li> <li>• Input Power: 62W - 190W</li> <li>• Operating temperature: -40°C up to 50°C</li> <li>• 0-10V dimming to 10%</li> <li>• Low-profile, lightweight design -14 lbs.</li> <li>• Universal mounting</li> </ul> | <ul style="list-style-type: none"> <li>• Multi-Level /Programmable occupancy sensing</li> <li>• IP65 optical assembly</li> <li>• 5-year limited warranty with optional 10-year limited warranty</li> <li>• Onboard emergency battery backup</li> <li>• Factory-installed cords and plugs up to 20'</li> <li>• Optional Synapse® SimplySNAP® wireless controls</li> </ul> |
|--|--|

**APPLICATIONS:** Industrial, warehouse, manufacturing, retail, grocery and gymnasiums



## HXB Series

Replaces 750W and 1000W HID fixtures.

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• 70 CRI; 80 CRI</li> <li>• CCT: 3500K, 4000K, 5000K</li> <li>• 35,000 and 70,000 lumens</li> <li>• Up to 150 LPW</li> <li>• Input Power: 276W - 485W</li> <li>• 0-10V dimming to 10%</li> </ul> | <ul style="list-style-type: none"> <li>• Operating temperature: -40°C to +60°C</li> <li>• Universal mounting: hook &amp; cord or pendant mount</li> <li>• Input Voltage: 120-277V (UL), 347-480V (UH)</li> <li>• 10-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Industrial, warehouse, manufacturing, grocery, gymnasium and retail spaces



Opaque Glare Shield Uplight



Translucent Glare Shield Uplight





## Cree Edge™ Series High Output

Replaces multiple 1000W MH fixtures.

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• 70 CRI (4000K &amp; 5700K); 90 CRI (5000K)</li><li>• CCT: 5700K standard, 5000K, 4000K</li><li>• Up to 76,123 lumens</li><li>• Input Power: 267W – 831W</li></ul> | <ul style="list-style-type: none"><li>• Cree TrueWhite® Technology on 5000K luminaires</li><li>• 0-10V dimming to 5%</li><li>• 10-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Retail and industrial high-bay, airport hangars, and gymnasiums



## 304 Series™

Replaces up to 320W MH fixtures.

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• 70 CRI</li><li>• CCT: 4000K, 5700K</li><li>• Input Power: 46W – 101W</li><li>• UL wet listed</li><li>• Multi-Level options</li></ul> | <ul style="list-style-type: none"><li>• IC rated and non-IC rated available</li><li>• Modular, low-profile design</li><li>• 10-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Interior high-bay or low-bay, convenience stores, warehouses and gymnasiums



# LED LAMPS



Soft accents or dramatic highlights — Cree® Pro Series LED lamps offer design freedom with beautiful, high-impact illumination for every lamp application.



## A19 Pro Series

40W, 60W and 75W equivalent.

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• 90 CRI</li><li>• CCT: 2700K, 3000K, 4000K (60W only), 5000K</li><li>• 460 - 1600 lumens</li><li>• Up to 91 LPW</li><li>• Input Power: 5.5W, 10W, 12W, 15W</li></ul> | <ul style="list-style-type: none"><li>• 25,000 hour rated lifetime</li><li>• Dimmable to 5% with select dimmers</li><li>• Suitable for damp locations</li><li>• Good for enclosed use (except 100W)</li><li>• 5-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Residential, hospitality, retail and grocery



## A21 Pro Series

100W and 125W equivalent.

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>• 90 CRI</li><li>• A21 100W: 2700K, 3000K, 5000K</li><li>• A21 3-way: 2700K</li><li>• Up to 2000 lumens</li><li>• Up to 94 LPW</li><li>• Input Power: 17W, 18W</li></ul> | <ul style="list-style-type: none"><li>• 25,000 hour rated lifetime</li><li>• Dimmable to 5% with select dimmers</li><li>• Suitable for damp locations</li><li>• 5-year limited warranty</li></ul> |
|--|---|

**APPLICATIONS:** Hospitality, retail, grocery and residential



# BR Pro Series



R20



BR30



BR40

- 90 CRI
- 25,000 hour rated lifetime
- Suitable for damp locations
- Dimmable to 5% with select dimmers
- 5-year limited warranty

**APPLICATIONS:** Residential, hospitality, retail and grocery

## R20 50W and 75W equivalent

- CCT: 2700K, 5000K
- 560, 980 lumens
- Up to 80 LPW
- Input Power: 7W, 13W

## BR30 65W and 100W equivalent

- BR30 65W: 2700K, 3000K, 4000K
- BR30 100W: 2700K, 3000K, 5000K
- 665, 1400 lumens
- Up to 88 LPW
- Input Power: 8.8W, 16W

## BR40 120W equivalent

- BR40 120W: 2700K, 3000K, 5000K
- 1750 lumens
- 76 LPW
- Input Power: 23W



# B11 Candelabra Pro Series



**25W, 40W and 60W equivalent.**

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• 90 CRI</li><li>• CCT: 2700K, 5000K</li><li>• 220, 300, 515 lumens</li><li>• Up to 97 LPW</li><li>• Input Power: 2.6W - 5.3W</li><li>• 15,000 hours rated lifetime</li><li>• E12 candelabra base</li></ul> | <ul style="list-style-type: none"><li>• Decorative Glass Filament</li><li>• Dimmable to 5% with select dimmers</li><li>• Suitable for damp locations</li><li>• Good for enclosed use (25W, 40W)</li><li>• 5-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Chandeliers, lamps and ceiling fan fixtures







PAR30S



PAR30L



PAR38

## PAR Pro Series

- Up to 50,000 hours rated lifetime
- CCT: 2700K, 3000K, 4000K
- Up to 92 LPW
- Multiple beam angles available: 15°, 25°, 40°
- Dimmable to 5% with select dimmers
- Suitable for Wet Locations (PAR38)
- 5-year limited warranty

**APPLICATIONS:** Hospitality, restaurants, retail, grocery and residential

Lamps available:

**PAR20 50W equivalent**

**PAR30 Short 75W equivalent**

**PAR30 Long 75W equivalent**

**PAR38 120W equivalent**

**PAR38 150W equivalent**

**PAR38 250W equivalent**



MR16



GU10

## MR Lamps

- 90 CRI
- 25,000 hour rated lifetime
- CCT: 2700K, 3000K
- Multiple beam angles available: 15°, 25°, 35°
- GU5.3 12V, GU10 120V Input
- Suitable for damp locations
- Smooth dimming
- 5-year limited warranty

**APPLICATIONS:** Hospitality, restaurants, retail, grocery and residential

Lamps available:

**MR16 50W equivalent**

**MR16 75W equivalent**





# LED TRACK LIGHTING



*LED Integrated Track Heads*

The Essentia® Series is well-designed and well-made to deliver exceptional track lighting.



## Essentia® Series Beveled Cylinder LED Track Head

Replaces standard halogen and incandescent track heads.

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• 80 CRI</li> <li>• CCT: 3000K, 3500K, 4000K</li> <li>• 1000 lumens</li> <li>• Input Power: 15W (75W equivalent)</li> <li>• Available in White, Black and Silver finishes</li> </ul> | <ul style="list-style-type: none"> <li>• 20° spot reflector with optional 40° diffuser included</li> <li>• Dimmable to 10%</li> <li>• Designed to last 35,000 hours</li> <li>• 3-year limited warranty</li> </ul> |
|---|---|

**APPLICATIONS:** Indoor residential, commercial, retail or industrial



## Essentia® Series Mini Flat Back LED Track Head

Replaces standard halogen and incandescent track heads.

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• 80 CRI</li> <li>• CCT: 2700K, 3000K, 3500K, 4000K</li> <li>• 500 lumens</li> <li>• Input Power: 8W</li> <li>• Available in White, Black and Silver finishes</li> </ul> | <ul style="list-style-type: none"> <li>• 36° beam angle</li> <li>• Utilizes Cree LEDs</li> <li>• Designed to last 30,000 hours</li> <li>• 3-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Indoor commercial, residential, retail or industrial



12" Wall Washer



24" Wall Washer

Both shown with louver and track accessory

# Essentia® Series Wall Wash Track Head

Replaces standard halogen, incandescent and fluorescent track heads.

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• 80 CRI</li><li>• CCT: 2700K, 3000K, 3500K, 4000K</li><li>• 3000 lumens: 12" Wall Wash</li><li>• 6000 lumens: 24" Wall Wash</li><li>• Up to 100 LPW</li></ul> | <ul style="list-style-type: none"><li>• Input Power: 30W (39W CMH equivalent); 60W (70W CMH equivalent)</li><li>• Dimmable to 10% using compatible TRIAC dimmers</li><li>• Designed to last 55,000 hours at 25°</li><li>• Five-year limited warranty</li></ul> |
|--|--|

APPLICATIONS: Indoor commercial, retail and hospitality



# Essentia® Series Track Systems

Replaces standard one- and two-circuit track systems.

- |   |  |
|---|--|
| <ul style="list-style-type: none"><li>• One- and two-circuit track</li><li>• Extensive collection of connectors available</li><li>• Available in White, Black and Silver finishes</li><li>• 4, 6 and 8 feet</li></ul> | <ul style="list-style-type: none"><li>• Fixtures can be surface or pendant mounted</li><li>• UL and cUL listed</li><li>• One-year limited warranty</li></ul> |
|---|--|

APPLICATIONS: Indoor commercial, retail and hospitality



# Essentia® Series Front Loading Gimbal Ring Track Head

Replaces standard halogen and incandescent gimbal ring track heads.

<ul style="list-style-type: none"><li>• Lamp compatibility: PAR38 maximum 150W</li><li>• Die-cast aluminum housing and polyester powder coated finish</li><li>• UL and cUL listed</li><li>• Easy relamping from the front of the gimbal ring</li></ul>	<ul style="list-style-type: none"><li>• Line voltage - medium base</li><li>• Recommended lamp: Cree PAR38</li><li>• One-year limited warranty</li></ul>
--	---

APPLICATIONS: Indoor commercial, retail or industrial



# Essentia® Series Rear Loading Gimbal Ring Track Head

Replaces standard halogen and incandescent rear-loading gimbal ring track heads.

<ul style="list-style-type: none"><li>• Lamp compatibility: PAR20, PAR30, PAR38</li><li>• Deep-drawn steel housing with U-shaped double yoke and polyester powder coated finish</li><li>• Line voltage - medium base</li></ul>	<ul style="list-style-type: none"><li>• Fixture relamps from the back of the ring</li><li>• UL and cUL listed</li><li>• One-year limited warranty</li></ul>
--	---

APPLICATIONS: Indoor commercial, retail or industrial



# Essentia® Series Flat Back Line Voltage Track Head

Replaces standard line voltage track heads.

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Lamp compatibility: PAR20, BR30, PAR30L</li><li>• Deep-drawn steel round back housing and polyester powder coated finish</li><li>• Line voltage - medium base</li></ul> | <ul style="list-style-type: none"><li>• This classic shape has a U-shaped double yoke with a single-locking knob to secure the aiming angle</li><li>• UL and cUL listed</li><li>• One-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Indoor commercial, retail or industrial





# TRACK ACCESSORIES
















## Essentia® Series Track Accessories

- Accessories including adaptors, connectors, clips, collars, caps and covers
- For use with all Essentia® Series track products
- For either one-circuit or two-circuit applications
- Available in White, Black and Silver finishes
- One-year limited warranty

### *Current Limiters, Power Feeds and Circuit Breakers*

<p>Current Limiter In-Line Adjustable Power Feed</p> 	<p>Current Limiter End Power Feed</p> 
<p>Title 24 Compliant Current Limiter In-Line Adjustable Power Feed</p> 	<p>Title 24 Compliant Current Limiter End Power Feed</p> 
<p>Current Limiter Mini End Power Feed</p> 	<p>Title 24 Compliant Current Limiter Mini End Power Feed</p> 
<p>Circuit Breakers</p> 	<p>Cord &amp; Plug Feed</p> 
<p>Floating Feed</p> 	<p>Conduit Feed</p> 

*Current Limiters, Power Feeds and Circuit Breakers*

<p>Outlet Box Feed</p> 	<p>T-Bar End Feed</p> 
<p>End Feed</p> 	<p>Adjustable Connector/Feed</p> 
<p>"T" Connector Feed</p> 	<p>"X" Connector</p> 
<p>T-Bar Adjustable Connector/Feed</p> 	<p>Mini Straight Connector</p> 
<p>Outlet Box Cover</p> 	<p>Midpoint Mounting</p> 
<p>T-Bar Attachment Clips (Flush Tiles)</p> 	<p>T-Bar Attachment Clips (Drop Tiles)</p> 
<p>Pendant Adaptor</p> 	




# LED AREA





Diverse lighting options featuring NanoOptic® Technology for parking lots, roadways, pathways, security areas and flood applications.



## Noctura Series

Replaces up to 1000W MH fixtures\*

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• Minimum 70 CRI</li> <li>• CCT: 4000K, 5000K</li> <li>• Up to 35,600 lumens</li> <li>• Up to 155 LPW</li> <li>• Input Power: 75W – 230W</li> <li>• Versatile mounting: Direct Arm, Adjustable Arm and Trunnion</li> </ul> | <ul style="list-style-type: none"> <li>• Suitable for wet locations</li> <li>• Enclosure meets IP65 requirements per IEC 60529</li> <li>• 1.5G Vibration certified</li> <li>• NEMA® 3-Pin Photocell Receptacle available</li> <li>• 5-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Parking lots, security, site pathway and general site lighting



## XSP Series

Replaces up to 400W MH fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• Minimum 70 CRI</li> <li>• CCT: 2700K, 3000K, 4000K, 5000K, 5700K</li> <li>• Up to 23,800 lumens</li> <li>• Up to 139 LPW</li> <li>• Input Power: 43W – 184W</li> <li>• NanoOptic® Precision Delivery Grid™ optic</li> </ul> | <ul style="list-style-type: none"> <li>• Designed with 0-10V dimming capabilities</li> <li>• cULus listed</li> <li>• Utility label and NEMA® 7-Pin Photocell Receptacle</li> <li>• 10-year limited warranty</li> </ul> |
|--|--|

**APPLICATIONS:** Parking lots, walkways and general area spaces





## OSQ High Output Series

**Replaces multiple 1000W MH fixtures.\***

- Minimum 70 CRI (3000K, 4000K, 5700K); 90 CRI (5000K)
- CCT: 3000K, 4000K, 5000K, 5700K
- Up to 68,691 lumens
- Up to 125 LPW
- Input Power: 341W - 550W
- Adjustable Arm, Direct Arm, and Transportation Mounts available
- Programmable Multi-Level option
- IP66 rated
- 3G Vibration certified
- Colorfast DeltaGuard® finish
- Optional NEMA® 7-Pin Photocell Receptacle
- 10-year limited warranty
- Optional Synapse® SimplySNAP controls

**APPLICATIONS:** Auto dealerships, parking lots, campuses, facade lighting, high-mast and general site lighting



## OSQ Series (Medium & Large)

**Replaces up to 1000W MH fixtures.\***

- Minimum 70 CRI (3000K, 4000K & 5700K); 90 CRI (5000K)
- CCT: 3000K, 4000K, 5000K, 5700K
- Up to 27,103 lumens
- Up to 139 LPW
- Input Power: 53W - 215W
- NanoOptic® Precision Delivery Grid™ optic
- Versatile mounting
- Adjustable Arm, Direct Arm, Transportation and Trunnion Mounts available
- Programmable Multi-Level options
- IP66 rated
- 3G Vibration certified
- Colorfast DeltaGuard® finish
- 10-year limited warranty
- Optional NEMA® 7-Pin Photocell Receptacle
- Optional Synapse® SimplySNAP controls

**APPLICATIONS:** Parking lots, walkways, campuses, auto dealerships, general site lighting and internal roadways





## THE EDGE® Series

**Replaces multiple 1000W MH fixtures.\***

- Minimum 70 CRI (4000K & 5700K); 90 CRI (5000K)
- CCT: 4000K, 5000K (High Output), 5700K
- Up to 85,638 lumens
- Input Power: 25W – 831W
- Utilizes Cree TrueWhite® Technology
- Suitable for wet locations
- Programmable Multi-Level options
- Modular, low-profile design
- 3G Vibration certified
- Colorfast DeltaGuard® finish
- Optional NEMA® 7-Pin Photocell Receptacle
- 10-year limited warranty

**APPLICATIONS:** Auto dealerships, large parking lots, campuses, facade lighting and general site lighting applications



## THE EDGE® Series Round

**Replaces up to 400W MH or HPS fixtures.\***

- Minimum 70 CRI
- CCT: 4000K, 5700K
- Up to 25,065 lumens
- Input Power: 46W – 202W
- Suitable for wet locations
- Modern, low-profile design
- Colorfast DeltaGuard® finish
- 10-year limited warranty

**APPLICATIONS:** Campus pathway, parking facilities



## THE EDGE® Series Pathway

**Replaces up to 100W PSMH or 100W HPS fixtures.\***

- Minimum 70 CRI
- CCT: 4000K, 5700K
- Up to 2,716 lumens
- Input Power: 22W – 40W
- Suitable for wet locations
- Two-Level options
- Multiple heights available
- Colorfast DeltaGuard® finish
- 10-year limited warranty

**APPLICATIONS:** Landscape, walkways and general site lighting

\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.

# LED DECORATIVE STREET & ROADWAY



Maintain the day form, but modernize the incumbent technology with energy-efficient, low-maintenance LED solutions from Cree Lighting.



## DPT Series

Replaces up to 70W MH or HPS and up to 175W Mercury Vapor fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 3000K, 4000K</li><li>• Up to 3,780 lumens</li><li>• Input Power: 34W</li><li>• Input Voltage: Integral 120-277V, 50/60Hz</li></ul> | <ul style="list-style-type: none"><li>• Utilizes a standalone UL 1598 compliant light engine</li><li>• Made with Cree Lighting LED technology</li><li>• 10-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Decorative street, pathway and general area lighting



DPT luminaire shown mounted to an enabling luminaire base



DPT Series with optional Backlight Control Shield accessory: DPT-BLS





# LED Post-Top Upgrade Kit

Replaces up to 175W MH or 150W HPS fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 2700K, 4000K</li><li>• Up to 6,400 lumens</li><li>• Input Power: 65W – 97W</li><li>• 0-10V dimming option</li></ul> | <ul style="list-style-type: none"><li>• Field Adjustable Output for increased flexibility</li><li>• Reuses most of existing luminaire for little waste</li><li>• 10-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Decorative street, pathway and general area lighting

**BXRAAA**  
Kit for Holophane®  
Granville Acorn



**BXRAAB**  
Kit for Holophane®  
Washington PostLite® Acorn



**BXRAAD**  
Kit for King Luminaire  
Washington Acorn



**BXRAAE**  
Kit for Holophane®  
Esplanade® Teardrop



**BXRAAF**  
Kit for Lumec® New  
Westminster Globe



**BXRAAH**  
Kit for Holophane® Granville  
Utility Acorn w/ Hinged Door



**BXRAAK**  
Kit for Holophane® Granville  
Utility Acorn w/ Removable Door



\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.



# LED STREET & ROADWAY



From rural streets to major highways, we have economical LED street lighting solutions that reduce energy and maintenance costs without sacrificing illumination performance.



## RSW Series

Replaces up to 400W HPS fixtures.\*

- 80 CRI (Small & Medium); 70 CRI
- CCT: 2700K (Small & Medium), 3000K, 4000K, 5000K
- Up to 31,300 lumens
- Up to 128 LPW
- Input Power: 26W – 244W
- Utilizes WaveMax® Technology
- IP66 rated optic box and driver
- Lightweight and easy to install
- Utility label and NEMA® 7-Pin Photocell Receptacle
- 10-year limited warranty

**APPLICATIONS:** Residential, local/collector roadways, intersections, major roads and highways



## XSP Series

Replaces up to 400W HPS fixtures.\*

- Minimum 70 CRI
- CCT: 2700K, 3000K, 4000K, 5000K, 5700K
- Up to 23,800 lumens
- Up to 139 LPW
- Input Power: 43W – 184W
- NanoOptic® Precision Delivery Grid™ optic
- Designed with 0-10V dimming capabilities
- cULus listed
- Utility label and NEMA® 7-Pin Photocell Receptacle
- 10-year limited warranty

**APPLICATIONS:** Street lighting – from residential streets to major roadways





From driveway to highway, communities are saving up to 70% on energy costs while enhancing driver and pedestrian safety.



# Traveyo Series

Replaces up to 400W HPS fixtures.\*

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 2700K, 3000K, 4000K, 5000K</li><li>• Up to 32,600 lumens</li><li>• Up to 155 LPW</li><li>• Input Power: 17W – 219W</li></ul> | <ul style="list-style-type: none"><li>• Lightweight and easy to install</li><li>• Utility label and NEMA® 7-Pin Photocell Receptacle</li><li>• 5-year limited warranty; optional 10-Year Limited Warranty</li></ul> |
|--|---|

**APPLICATIONS:** Residential, local/collector roadways, intersections, major roads and highways



# RUL Series

Replaces up to 100W HPS or 100W to 175W Mercury Vapor fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 3000K, 4000K</li><li>• Up to 5,682 lumens</li><li>• Up to 114 LPW</li><li>• Input Power: 50W</li><li>• Suitable for wet locations</li></ul> | <ul style="list-style-type: none"><li>• Significant energy and maintenance savings</li><li>• Easy installation</li><li>• Utility label and NEMA® 3-Pin Photocell Receptacle</li><li>• Utility kits available</li><li>• 10-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Rural and residential street lighting, agricultural, general security and loading/receiving areas



RUL luminaire shown with reflector/  
refractor included in ES-K2 option





# LEDway® High Output Series

Replaces up to 400W HPS fixtures.\*

- |   |  |
|---|--|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 3000K, 5700K</li><li>• Up to 28,462 lumens</li><li>• Input Power: 136W or 274W</li><li>• Suitable for wet locations</li></ul> | <ul style="list-style-type: none"><li>• Field Adjustable Output option</li><li>• Utility option</li><li>• 10-year limited warranty</li></ul> |
|---|--|

**APPLICATIONS:** Street lighting – from local/collector streets to major roadways



# LEDway® Series

Replaces up to 250W HPS fixtures.\*

- |  |   |
|--|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 4000K, 5700K</li><li>• Up to 24,717 lumens</li><li>• Input Power: 35W – 274W</li></ul> | <ul style="list-style-type: none"><li>• Suitable for wet locations</li><li>• Modular design</li><li>• Utility option</li><li>• 10-year limited warranty</li></ul> |
|--|---|

**APPLICATIONS:** Street lighting – from residential streets to major roadways

\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.

## LED CANOPY & SOFFIT



Cree Lighting recessed canopy and soffit luminaires efficiently light the way to exterior sites, surrounding areas and interior high-bay applications leading to an overall low total cost of ownership.



Flat Lens



Drop Lens

## CPY Series

Replaces up to 400W HID fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 3000K, 4000K, 5700K</li><li>• Up to 20,080 lumens</li><li>• Input Power: 31W – 145W</li><li>• Direct, pendant or hook and cord mount</li><li>• Flat or drop lenses available</li></ul> | <ul style="list-style-type: none"><li>• Class I, Division II Hazardous Location rating</li><li>• Programmable Multi-Level option</li><li>• Easy and quick installation</li><li>• IP66 rated</li><li>• Upgrade Kit options</li><li>• 10-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Petroleum stations, convenience stores, drive-thru banks, restaurants, retail and grocery, industrial low-bay and high-bay



## 228 Series™

Replaces up to 400W HID fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 4000K, 5700K</li><li>• Up to 21,486 lumens</li><li>• Input Power: 54W – 201W</li><li>• UL wet listed</li></ul> | <ul style="list-style-type: none"><li>• Programmable Multi-Level option</li><li>• Upgrade kit options</li><li>• Modular, flush mount design</li><li>• 10-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Petroleum stations, convenience stores, drive-thru banks and restaurants, retail and grocery






## 304 Series™

Replaces up to 320W HID fixtures.\*

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• 70 CRI</li> <li>• CCT: 4000K, 5700K</li> <li>• Up to 13,697 lumens</li> <li>• Input Power: 46W – 135W</li> <li>• Suitable for wet locations</li> <li>• Enclosure meets IP66 requirements</li> </ul> | <ul style="list-style-type: none"> <li>• Driver centrally located</li> <li>• Convenient electrical inspection access from below</li> <li>• Modular, flush mount design</li> <li>• 10-year limited warranty</li> </ul> |
|--|---|

**APPLICATIONS:** Petroleum stations, convenience stores, drive-thru banks and restaurants, retail and grocery



## THE EDGE® Series

Replaces up to 700W HID fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• 70 CRI</li> <li>• CCT: 4000K, 5700K</li> <li>• Up to 35,841 lumens</li> <li>• Input Power: 46W – 263W</li> <li>• Suitable for wet locations</li> </ul> | <ul style="list-style-type: none"> <li>• Enclosure meets IP66 requirements</li> <li>• Programmable Multi-Level option</li> <li>• Modular, low-profile design</li> <li>• 10-year limited warranty</li> </ul> |
|---|---|

**APPLICATIONS:** Petroleum canopies, medium-high bay general lighting and soffits




\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.





# LED PARKING STRUCTURE



First impressions start in the garage. Cree Lighting parking structure luminaires make it a better one by providing clean, uniform, low-glare illumination with superior performance that enhances safety and visibility.



## IG Series

Replaces up to 175W HID fixtures.\*

- Minimum 80 CRI
- CCT: 3000K, 3500, 4000K, 5700K
- Up to 7,550 lumens
- Up to 126 LPW
- Input Power: 33W or 60W
- Utilizes WaveMax® Technology
- Designed with 0-10V dimming capabilities standard (non-PML)
- Suitable for wet locations
- IP66 rated
- Precise low-glare optics
- Programmable Multi-Level option
- 10-year limited warranty
- **Optional Synapse® SimplySNAP controls**

### Coming Soon:

Limelight by Lutron wireless controls

APPLICATIONS: Parking structure



## VG Series

Replaces up to 175W HID fixtures.\*

- Minimum 70 CRI
- CCT: 3000K, 4000K, 5700K
- Up to 5,700 lumens
- Input Power: 33W or 54W
- Suitable for wet locations
- IP66 rated
- Low glare, indirect view LEDs
- Programmable Multi-Level option
- 10-year limited warranty

APPLICATIONS: Parking structures





# 304 Series™

Replaces up to 320W HID fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 4000K, 5700K</li><li>• Up to 13,712 lumens</li><li>• Input Power: 46W – 135W</li><li>• UL wet listed</li><li>• IP66 rated</li></ul> | <ul style="list-style-type: none"><li>• Programmable Multi-Level option</li><li>• Integrated occupancy sensor</li><li>• Low-profile design</li><li>• 10-year limited warranty</li></ul> |
|---|---|

APPLICATIONS: Parking structures



\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.



LED FLOOD





Cree Lighting luminaires for flood and sign lighting provide specific distributions of light for showcasing horizontal and vertical sign surfaces and architectural features.



## Noctura Series

Replaces up to 400W MH fixtures\*

- Minimum 70 CRI
- CCT: 4000K, 5000K
- Up to 28,400 lumens
- Up to 158 LPW
- Input Power: 12W – 186W
- Enclosure meets IP65 requirements per IEC 60529
- Suitable for wet locations
- Versatile mounting: Small - Knuckle, Yoke Large - Adjustable Arm, Trunnion
- NEMA® 3-Pin Photocell Receptacle available
- 5-year limited warranty

**APPLICATIONS:** Accent, sign or building facades



OSQ Series

## OSQ Series

Replaces up to 1000W MH fixtures.\*

- Minimum 70 CRI (3000K, 4000K & 5700K); 90 CRI (5000K)
- CCT: 3000K, 4000K, 5000K, 5700K
- Up to 27,103 lumens
- Input Power: 53W – 215W
- Up to 139 LPW
- NanoOptic® Precision Delivery Grid™ optic
- Adjustable Arm, Direct Arm, Transportation and Trunnion Mounts available
- Programmable Multi-Level options
- IP66 rated
- 3G Vibration certified
- Colorfast DeltaGuard® finish
- Optional NEMA® 7-Pin Photocell Receptacle
- 10-year limited warranty

**APPLICATIONS:** Parking lots, walkways, campuses, auto dealerships and building façades





OSQ Series Utility  
UA Mount

## OSQ Series Utility

Replaces up to 1000W MH fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 3000K, 4000K</li><li>• Up to 26,583 lumens</li><li>• Input Power: 53W – 215W</li><li>• 45° Utility Arm (with Cord Side or End Exit); Direct Arm, or Trunnion Mounts available</li></ul> | <ul style="list-style-type: none"><li>• Utility label &amp; NEMA® 7-Pin Photocell Receptacle included</li><li>• Suitable for wet locations</li><li>• 3G Vibration certified</li><li>• Colorfast DeltaGuard® finish</li><li>• 10-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Parking lots, walkways, campuses, auto dealerships and building façades – designed for utilities



## 304 Series™

Replaces up to 250W HID fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI</li><li>• CCT: 4000K, 5700K</li><li>• Up to 13,712 lumens</li><li>• Input Power: 46W – 135W</li><li>• UL wet listed</li></ul> | <ul style="list-style-type: none"><li>• Programmable Multi-Level option</li><li>• Modular, low-profile design</li><li>• 10-year limited warranty</li></ul> |
|--|--|

**APPLICATIONS:** Underpasses and sign lighting

\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.



THE EDGE® High Output Flood



THE EDGE® Flood Square

## THE EDGE® Series

Replaces multiple 1000W MH fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"><li>• Minimum 70 CRI (4000K &amp; 5700K); 90 CRI (5000K)</li><li>• CCT: 4000K, 5000K (High Output), 5700K</li><li>• Up to 85,638 lumens</li><li>• Input Power: 25W – 831W</li><li>• Suitable for wet locations</li><li>• Programmable Multi-Level options</li></ul> | <ul style="list-style-type: none"><li>• Modular, low-profile design</li><li>• IP66 rated (select versions)</li><li>• 3G Vibration certified</li><li>• Colorfast DeltaGuard® finish</li><li>• Optional NEMA® Photocell Receptacle</li><li>• 10-year limited warranty</li></ul> |
|---|---|

**APPLICATIONS:** Parking lots, walkways, campuses, auto dealerships and building façades



# LED WALL MOUNT



Sleek and stylish security and perimeter lighting features a low-profile design that provides clean, uniform illumination for increased visibility and a secure environment.



## Noctura Series

Replaces up to 400W MH fixtures\*

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• Minimum 70 CRI</li> <li>• CCT: 4000K, 5000K</li> <li>• Up to 22,600 lumens</li> <li>• Input Power: 12W – 148W</li> </ul> | <ul style="list-style-type: none"> <li>• Suitable for wet locations</li> <li>• Enclosure meets IP65 requirements per IEC 60529</li> <li>• 5-year limited warranty</li> </ul> |
|---|--|

**APPLICATIONS:** Building facades, security, general outside lighting



## XSP Series

Replaces up to 250W MH fixtures.\*

- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• Minimum 70 CRI (3000K, 4000K &amp; 5700K); 90 CRI (5000K)</li> <li>• CCT: 3000K, 4000K, 5000K, 5700K</li> <li>• Up to 8,475 lumens</li> <li>• Input Power: 19W – 78W</li> <li>• Suitable for wet locations</li> </ul> | <ul style="list-style-type: none"> <li>• IP66 rated</li> <li>• Multi-Level options</li> <li>• Utilizes Cree TrueWhite® Technology</li> <li>• 10-year limited warranty</li> </ul> |
|--|--|

**APPLICATIONS:** Security and perimeter outside lighting



## THE EDGE® Series

Replaces up to 320W MH fixtures.\*

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>• Minimum 70 CRI</li> <li>• CCT: 4000K, 5700K</li> <li>• Up to 16,074 lumens</li> <li>• Input Power: 25W – 134W</li> <li>• Suitable for wet locations</li> </ul> | <ul style="list-style-type: none"> <li>• Modular, low-profile design</li> <li>• IP66 rated</li> <li>• Colorfast DeltaGuard® finish</li> <li>• 10-year limited warranty</li> </ul> |
|---|---|

**APPLICATIONS:** Security and perimeter outside lighting



\*Replacements are general recommendations only. They can vary dependent upon application and optical performance requirements. Consult factory for specific product recommendation based on application.



# CREE LIGHTING TECHNOLOGY



## THE SMARTCAST INTELLIGENCE PLATFORM™

Wherever the lights, whatever the environment, the SmartCast Intelligence Platform™ enables advanced lighting control and limitless business applications with value far beyond lighting.

---

### Simply Intuitive, Advanced Lighting Control—Everywhere.

Featuring an intuitive, simple design and user experience for operation, commissioning and data collection, the SmartCast Intelligence Platform™ brings scalable, intelligent lighting networks to every space, delivering energy savings of 70% or more and a highly personalized lighting experience.

### An Open System That Supports SmartCast® and 3rd-Party Technologies.

This isn't another proprietary "black-box" system that locks you into costly vendor charges for upgrades or inter-network connectivity. BACnet integration and a ReST-based application programming interface (API) open the door to virtually unlimited applications through seamless connectivity with enterprise networks, building management software and the Internet of Things.

### A Secure Architecture.

Designed with security in mind from day one, the SmartCast Intelligence Platform™ employs industry-standard encryption to protect data streams, SmartCast® luminaires and other network endpoints. End users always retain control over access privileges, enabled applications and data streams shared with third parties. Software and security updates? They're seamless.

### Business Value Far Beyond Lighting.

Add SmartCast Advisor®, and the platform lets you turn data into dollars from day one with occupancy-based space optimization and situational awareness. For the future, the SmartCast Intelligence Platform™ is ready to pioneer data-driven applications that help businesses become more agile, productive and profitable.


## So Easy, the Building of the Future Can Be the One You're Already In.

### ENVIRONMENTAL AWARENESS AND CONTROL

Embedded sensors continually detect and share data on room occupancy and ambient light to fine-tune your environment and energy-saving strategies in real time.

### SIMPLE SET-UP AND COMMISSIONING

OneButton™ Setup commissions hundreds of luminaires in a single step, providing smart lighting that meets existing and emerging buildings codes, wirelessly and over Power over Ethernet (PoE) — live in minutes, not weeks.





### VALUE BEYOND LIGHTING

SmartCast® Technology creates secure lighting networks that connect seamlessly with other building management systems and with third-party IoT systems for even more value.

### A PLATFORM FOR INTELLIGENT LIGHTING

SmartCast® Technology orchestrates the optimal environment for energy efficiency and productivity by adjusting brightness and color temperatures to tasks and personal preferences, and tracking improvements.

## SmartCast® Technology Products

### CR SERIES ARCHITECTURAL TROFFERS



Integrated Motion Sensor



CR24™

See page 11 for more information.

### ZR COMMERCIAL SPEC TROFFERS



Integrated Motion Sensor



ZR24™

See page 11 for more information.

**SMARTCAST®**  
TECHNOLOGY



**LN SERIES SUSPENDED AMBIENT  
INDIRECT/DIRECT**



LN4™

See page 15 for more information.

**KR SERIES DOWNLIGHTS**



KR6™

See page 3 for more information.

**CS SERIES LINEAR LUMINAIRES**



CS14™

See page 16 for more information.



Configuration Tool



0-10V Interface



Plug Load Controller



Light Dimmer




CCT Dimmer


Visit [creelighting.com](http://creelighting.com) for additional offerings including Lutron EcoSystem® Enabled controls.

### WAVEMAX® TECHNOLOGY

WaveMax® Technology is a breakthrough in the execution of waveguide technology that challenges industry-standard assumptions of how light is delivered. Featuring up to 90% optical efficiency and precise optical control, WaveMax® Technology enables customers to obtain unmatched visual comfort and improved color quality without sacrificing performance. This transformative technology redefines the limits of fixture design to optimize performance and provides more aesthetic options at an unmatched customer value.



LN Series



IG Series



RSW Series



Before: Metal Halide Lighting



After: WaveMax® Technology LED Lighting

### COLORFAST DELTAGUARD® FINISH

Our exclusive Colorfast DeltaGuard® Finish protects our LED outdoor fixtures without compromise. Immersive conditioning across 18 stages delivers an e-coat epoxy primer with an ultra-durable powder topcoat, providing unmatched protection against corrosion, UV light, fading and weathering complete with a 10-year limited warranty.

### CREE TRUEWHITE® TECHNOLOGY

Cree TrueWhite® Technology provides exceptional color quality to lighting applications. Featuring a broad spectral power distribution, Cree TrueWhite® Technology delivers 90+ CRI, high R9 values, and accurate and consistent color. The result is high performing, beautiful white light that can dramatically improve the visual appearance of both interior and exterior spaces — all while offering significant energy savings compared to traditional technologies.



Before: Fluorescent Lighting



After: Cree TrueWhite® LED Lighting

### NANOOPTIC® TECHNOLOGY

With patented NanoOptic® Technology available in multiple distributions, Cree Lighting's outdoor LED fixtures provide precise optical control for exceptional application performance and energy savings. The NanoOptic® refractor system offers superior light control with more lumens delivered in the target area, improved uniformity ratios and controlled high-angle brightness.



High Pressure Sodium Lighting

THE EDGE® Series Lighting



Visit **[creelighting.com](http://creelighting.com)** or contact a  
Cree Lighting representative to learn more.

© 2020 Cree Lighting, A company of IDEAL INDUSTRIES. All rights reserved. For informational purposes only. Not a warranty or specification. See [creelighting.com/warranty](http://creelighting.com/warranty) for warranty and specifications. Essentia®, SmartCast®, Colorfast DeltaGuard®, NanoOptic®, LEDway®, Noctura®, THE EDGE®, Traveyo®, Smartcast Advisor® and WaveMax® are registered trademarks and Cadian™, Stylus™, Precision Delivery Grid™, OneButton™, KR8™, KR6™, CR4™, CR6™, LN4™, XSP™, 228 Series™, 304 Series™, SmartCast Intelligence Platform™, RUL™, and RSW™ are trademarks of IDEAL INDUSTRIES Lighting, LLC. Cree®, the Cree logo, TrueWhite®, Cree TrueWhite® and Cree TrueWhite Technology logo are trademarks of Cree, Inc. Lutron® and Lutron EcoSystem® are registered trademarks of Lutron Electronics Co. Lumec is a registered trademark of Lumec Inc. Holophane®, Esplanade®, and Washington PostLite® are registered trademarks of ABL IP Holding LLC. Synapse® is a registered trademark of Synapse Wireless, Inc.

CAT/CSJ-C004 Rev. Date 03/12/2020

**CREE**  **LIGHTING**