# 

For Professionals... Since 1857®





Klein Pliers ...... Pages 5-23







Wrenches . . . . . . . . . . . . Pages 123–138







Voice/Data/Video
Tools, Test, Kits
& Connectors .......Pages 33-54



Levels & Measuring Tools ....Pages 148–153





Fish Tapes,
Accessories
& Conduit Tools ......Pages 154–165





Personal Protective
Equipment &
Safety Products......Pages 167–178



**Insulated Tools** ...... Pages 70–84



Tool Pouches,
Carriers, Belts
& Suspenders.......Pages 179–198



Screwdrivers,
Nut Drivers
& Accessories ......Pages 85-116







**Lineman Buckets** 

& Accessories ..... Pages 214–221



Knives &

Cutting Tools ...... Pages 295–303



Block & Tackle . . . . Pages 222-226



Hammers, Chisels



**Wire Pulling** 



Electrical Test &

Measurement ...... Pages 308-326



**Steel Construction** 





Mining & **Heavy Industry** 

**Alphabetical** & Numeric

Indexes ...... Pages 333–352



**Sheet Metal** 



**Holemaking Products &** 

Accessories ....... Pages 278–289



**Saws & Blades** . . . . Pages 291–294



# **Company History**

Klein Tools was founded in 1857 by an industrious German immigrant, Mathias Klein, who began in the hand tool business when a broken side-cutting pliers was brought to his forge shop by a telegraph lineman. Mathias repaired the pliers by forging and finishing a new half for the tool and riveting it to the old half. Soon the lineman returned because the other original half of the pliers had broken and needed replacement. Mathias forged and finished the second half of the pliers and riveted it to the other replacement half — creating the first complete Klein pliers.

To this day, Klein Tools is proudly owned and managed by the Klein family. Over 150 years of hard work and dedication has earned Klein the reputation of supplying only the finest quality products for users of professional hand tools and occupational protective equipment.





Klein's reputation as a leading producer of professional-quality products is global. Klein Tools products are available worldwide through a well-established network of agents and distributors who stock what is needed for their particular markets.





# **Company History**

## **The Professional Difference**

These days, it can be hard to find companies that make products you can count on. But that's exactly what you'll get from Klein Tools.

We don't just make great products, we make great products that stand up to the demands of the professionals who use them everyday. Because our standards are as high as yours, we demand that every one of our hand tools delivers all the performance, durability and precision that you need to get the job done right.

And by using only the highest quality materials, superior workmanship, and keeping our manufacturing as close to home as we can, we're able to uphold those rigorous standards.

Klein isn't just the name of our company, it's also our family name, so we have to be proud of everything we make. And since we're an American company that's been family-owned and family-run, since 1857, you know you can count on us to be here tomorrow.

Just pick up a Klein tool and you'll know what all the professionals know...when you buy a Klein, it'll never let you down.

That's why we're the #1 choice of professional electricians in the US.





## Introduction — Pliers

#### **Klein Quality**

All Klein pliers are made of the finest U.S. steel alloy. They are forged, precision machined, hardened, and carefully tempered for maximum strength. Klein pliers provide exceptional performance and durability.

All pliers mating surfaces and dimensions are precision machined for faultless performance. Pliers halves are precision machined and hot riveted for uniformly smooth opening and closing action. Cutting knives are manufactured for long-lasting edges and perfect alignment.

The cutting knives on all Klein pliers are designed to meet according to the way each is used. Side-cutting and long-nose pliers with side cutters have

knives that meet at the hinge first and then meet at least one-half of the knife length. Diagonal-cutting pliers meet at the tip first and then meet at least one-half of the knife length.

These precise knife-closing designs increase knife life and facilitate resharpening.

Klein pliers are individually adjusted to meet performance standards far exceeding application requirements – ensuring that nothing less than outstanding quality ever carries the Klein name.

#### **Using Pliers**

A professional knows all the rules about using pliers, but a review of the following points may help you recall any you may have forgotten.

- 1. Never use pliers to do another tool's job. Pliers should not be used as a hammer or pry tool or a wrench. Using pliers instead of the proper tools risks damaging the work, damaging yourself, and losing time.
- 2. Never push pliers beyond their capacity. Bending stiff wire with light pliers or the tip of needle-nose pliers can spring them or break them. Use a stronger, blunt-nose pliers. When you need greater leverage, use pliers with greater leverage. Don't extend the length of the pliers handles. Bolts should be cut with a bolt cutter, and large cable with a cable cutter.
- **3. Never expose pliers to excessive heat.** Direct flame on metal can ruin the tool. Cutting pliers are especially vulnerable to high, direct heat.
- 4. Never cut hardened wire with ordinary pliers. Pliers should not be used for cutting hardened wire unless they are specifically recommended for this use.
- 5. Never rock pliers from side to side when cutting wire...and never bend the wire back and forth against the cutting knives. Either practice can dull or nick the cutting edges. Cut wire at a right angle only. If it won't cut readily, the knives may need sharpening. Or you may need pliers with greater leverage.

- 6. Never cut any wire or metal unless your eyes are protected. Goggles or other protective devices are an absolute must. Don't take shortcuts. Operate safely...the professional way.
- 7. Never cut any wire or metal unless your fellow workers' eyes are also protected. The wire that doesn't get you may get someone else. Think about the "other guy" as well as yourself.
- 8. Never depend on plastic-dipped handles to insulate you from electricity. Plastic-dipped and Journeyman<sup>TM</sup> handles are intended for comfort and a firmer grip only. They are not intended for protection against electric shock. Never use any pliers or cutting tools on live electrical circuits. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.
- 9. Always wear approved eye protection such as protective goggles or a face mask.

## **Pliers Catalog Number Prefixes/Suffixes**

"D" (Prefix) – Indicates the pliers have plastic-dipped handles. Plastic-dipped handles are for comfort, NOT for protection against electrical shock.

"HD" (Prefix) – Indicates the pliers have heavy-duty plastic-dipped handles. Heavy-duty plastic-dipped handles provide an extra level of user comfort and are NOT for protection against electrical shock.

- "J" (Prefix) Indicates the pliers have Journeyman™ handles. State-ofthe-art dual material molding that allows for a softer, more comfortable grip on the outer surface and a harder, more durable grip on the inner surface and handle ends.
- "C" (Suffix) Indicates the pliers have a coil spring in the handles for self-opening action.

## **Pliers Cutting Edges**

Knife-edge descriptions refer to the angle of the outside cutting edges of the knives when fully closed.

#### **Standard Cutting Edges**

Cuts hard wire. Found on all Klein side cutters, long nose, and on most diagonal-cutting pliers.



#### **Semi-Flush Cutting Edges**

Closely cuts medium wire. Found on select Klein diagonal cutting pliers.



#### **Full-Flush Cutting Edges**

Close, flat cutting of soft wire only. Found on select diagonal-cutting pliers.





# **Introduction – Pliers**

#### **Pliers Dimensions**

All Klein pliers are listed with necessary dimensions in both inches and millimeters. The following drawings of six basic types of pliers are keyed by letter to the dimensions given for each pliers listed. All dimensions are subject to commercial tolerances.


A – Overall Length

B – Jaw Length


C - Jaw Width

- D Jaw Thickness
- E Knife Length
- F Point Thickness







3. End-Cutting Pliers




5. Flat-Nose and Duck-Bill Pliers




2. Diagonal-Cutting Pliers



4. Long-Nose Pliers




6. Curved-Nose Pliers



Pliers dimensions shown are accurate within accepted commercial tolerances, which allow slight variations that normally result from forging and grinding operations.

# **Side-Cutting Pliers**



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



## High-Leverage Side-Cutting Pliers - Heavy-Duty Cutting

## 2000 SERIES

#### Additional Features:

- · Cuts ACSR, screws, nails and most hardened wire.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.
- Features combination polished and black-oxide finish.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
D2000-7	New England	7-7/8" (200 mm)	1-9/32" (33 mm)	1-1/32" (26 mm)	1/2" (13 mm)	3/4" (19 mm)	plastic-dipped	royal blue	.66
D2000-8	New England	8-11/16" (221 mm)	1-7/16" (37 mm)	1-7/64" (28 mm)	5/8" (16 mm)	3/4" (19 mm)	plastic-dipped	royal blue	.85
D2000-9NE	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.09
HD2000-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	heavy-duty, oversized, plastic-dipped	light red	1.15
Journeyman	™ 2000 Series	s – Dual-material l	nandles						
J2000-8	New England Tapered	8-13/16" (224 mm)	1-7/16" (37 mm)	1-7/64" (28 mm)	5/8" (16 mm)	3/4" (19 mm)	Journeyman	light blue/black	.93
J2000-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.13

Refer to the insulated section for insulated pliers.

## **High-Leverage Side-Cutting Pliers**

#### Additional Features:

 High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.

Streamlined design with sure-gripping, cross-hatched knurled jaws.



D213-9NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
D213-8NE	New England	8-11/16" (221 mm)	1-7/16" (37 mm)	1-3/16" (30 mm)	5/8" (16 mm)	23/32" (18 mm)	plastic-dipped	dark blue	.90
213-9NE	New England	9-1/4" (235 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plain	n/a	1.05
D213-9NE	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.14
HD213-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	heavy-duty, oversized, plastic-dipped	light red	1.15
Journeyma	n <sup>TM</sup> Series –	Dual-material han	dles						
J213-8NE	New England	8-13/16" (224 mm)	1-7/16" (37 mm)	1-3/16" (30 mm)	5/8" (16 mm)	23/32" (18 mm)	Journeyman	dark blue/black	0.97
J213-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.13
5 ( , ,,									

Refer to the insulated section for insulated pliers.

## **High-Leverage Side-Cutting Pliers**

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Sure-gripping, cross-hatched knurled jaws.



D213-9

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	<b>Handle Color</b>	Weight (lbs.)
D213-9	Square	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.07

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

## High-Leverage Side-Cutting Pliers -**Fish Tape Pulling**

#### Additional Features:

- Quickly and easily pulls 1/8" or 1/4" flat steel fish tape without damaging the tape.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)		
D213-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.06		
Journeyman™ Series – Dual-material handles											
J213-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.11		
2000 Series	* – Heavy-dut	y cutting knives									
D2000-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.09		
Journeyman	Journeyman™ 2000 Series* – Dual-material handles										
J2000-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.14		
*Cuts ACSR,	*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.										

## **High-Leverage Side-Cutting Pliers – Lineman's Bolt-Thread Holding**

#### Additional Features:

- Hinge opening holds and cleans 5/8" pole line and hardware bolts or threaded rods.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with rounded nose and sure-gripping, cross-hatched knurled jaw.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)	
D213-9NETH	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.12	
HD213-9NETH	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	heavy-duty, oversized, plastic-dipped	light red	1.18	
2000 Series*	2000 Series* – Heavy-duty cutting knives									
D2000-9NETH	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.18	

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## High-Leverage Side-Cutting Pliers — **Connector Crimping**

#### Additional Features:

- Crimping die behind hinge for superior leverage crimping of non-insulated connectors, lugs and terminals.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with rounded nose and sure-gripping, cross-hatched knurled jaws.





D213-9NECR

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight(lbs.)			
D213-9NECR	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	yellow	1.08			
Journeyman™ Series – Dual-material handles												
J213-9NECR	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	yellow/black	1.13			
2000 Series*	– Heavy-dut	y cutting knives										
D2000-9NECR	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.08			
Journeyman™ 2000 Series* – Dual-material handles												
J2000-9NECR	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.12			
*Cute ACSD	crowe paile	and most hardened	Lwire Features con	nhination nolicha	d and black-ovide	finich Defer to th	a inculated cactic	n for inculated n	liare			

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish. Refer to the insulated section for insulated pliers.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



## **Side-Cutting Pliers**

#### Additional Feature:

Sure-gripping, cross-hatched knurled jaws.



D201-9NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
Streamline	ed Design								
D201-7NE	New England	7-7/16" (189 mm)	1-9/32" (33 mm)	1-1/16" (27 mm)	1/2" (13 mm)	5/8" (16 mm)	plastic-dipped	dark blue	.55
D201-8NE	New England	8-11/16" (221 mm)	1-7/16" (37 mm)	1-3/16" (30 mm)	5/8" (16 mm)	23/32" (18 mm)	plastic-dipped	dark blue	.92
D201-9NE	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.09
Square No:	se								
D201-8	Square	8-11/16" (221 mm)	1-7/16" (37 mm)	1-7/32" (31 mm)	5/8" (16 mm)	23/32" (18 mm)	plastic-dipped	dark blue	.93
D201-9	Square	9-3/8" (238 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.10

# High-Leverage Universal Combination Pliers

#### Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals.
- Toothed pipe-grip for greater gripping power.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)		
12098	Universal	8-5/8" (219 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	17/32" (13 mm)	3/4" (19 mm)	plastic-dipped	dark blue	.72		
Journeyman™ Series – Dual-material handles											
J12098	Universal	8-3/4" (222 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	17/32" (13 mm)	3/4" (19 mm)	Journeyman	dark blue/black	.82		
			. ,		. ,	. ,	· · · · · · · · · · · · · · · · · · ·				

Refer to the insulated section for insulated pliers.

## Ironworker's Work Pliers - High-Leverage

#### Additional Features:

- Twists and cuts soft annealed rebar tie wire.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Hook bend handle.
- Spring-loaded action for self-opening.
- Heavy-duty knurled jaws.





D213-9ST

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)			
213-9ST	Square	9-1/4" (235 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plain	n/a	1.02			
D213-9ST	Square	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.10			
2000 Serie	2000 Series* – Heavy-duty cutting knives											
D2000-9ST	Square	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.10			
+0 1005		l	and and the Freehouse a	t- i ti ti - t-	and an all blanch and all a	Contact.						

\*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

## Ironworker's Work Pliers

#### Additional Features:

- Twists and cuts soft annealed rebar tie wire.
- Hook bend handle.
- Spring-loaded action for self-opening.
- Heavy-duty knurled jaws.




D201-7CST

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)		
201-7CST	Square	9-1/8" (232 mm)	1-9/32" (33 mm)	1-5/32" (29 mm)	1/2" (13 mm)	5/8" (16 mm)	plain	n/a	.65		
D201-7CST	Square	9-1/4" (235 mm)	1-9/32" (33 mm)	1-5/32" (29 mm)	1/2" (13 mm)	5/8" (16 mm)	plastic-dipped	dark blue	.75		
2000 Series	2000 Series* – Heavy-duty cutting knives										
D2000-7CST	Square	9-1/4" (235 mm)	1-9/32" (33 mm)	1-5/32" (29 mm)	1/2" (13 mm)	5/8" (16 mm)	plastic-dipped	royal blue	.70		

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

# **Diagonal-Cutting Pliers**



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



1

# **Diagonal-Cutting Pliers**

## **High-Leverage Diagonal-Cutting Pliers**

#### Additional Feature:

 High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



D2000-28

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D228-7	7-1/8" (181 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.54
D228-8	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.60
Journeyman™	Series – Dual-mat	terial handles						
J228-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.67
2000 Series*	- Heavy-duty cutti	ng knives						
D2000-28	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	royal blue	.60
Journeyman™	2000 Series* – Du	ıal-material hand	les					
J2000-28	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.67

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish. Refer to the insulated section for insulated pliers.

## High-Leverage Diagonal-Cutting Pliers — Angled Head

#### Additional Features:

- Angled head design for easy work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D248-8	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.60
D238-8	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	semi-flush**	plastic-dipped	red	.59
Journeyman S	eries – Dual-matei	rial handles						
J248-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.61
2000 Series* -	- Heavy-duty cutti	ng knives						
D2000-48	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	royal blue	.60
Journeyman 2	000 Series* – Dua	l-material handle	es					
J2000-48	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.61

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

# High-Leverage Diagonal-Cutting Pliers — Stripping Holes

#### Additional Features:

- Cleanly strips 12 and 14 solid AWG wire.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D243-8	8-1/16" (205 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.60

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



<sup>\*\*</sup>Semi-flush cutting knives cut Cherry Burrel rivets. For use on non-ferrous wire only.

Refer to the insulated section for insulated pliers.

# **Diagonal-Cutting Pliers**

#### High-Leverage Diagonal-Cutting Pliers - Ironworker's

#### Additional Features:

- Angled head design for easy working in confined spaces.
- Hooked handle for improved grip.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



D248-9ST

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D248-9ST	9-3/16" (233 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.68

## **Heavy-Duty Diagonal-Cutting Pliers – Tapered Nose**

#### Additional Features:

- Heavy-duty tapered nose design.
- One-inch jaws easily reach into confined spaces.

D220-7

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D220-7	7-11/16" (195 mm)	1" (25 mm)	31/32" (25 mm)	1/2" (13 mm)	standard	plastic-dipped	red	.54

Refer to the insulated section for insulated pliers.

## **Heavy-Duty Diagonal-Cutting Pliers — All Purpose**

#### Additional Features:

- Heavier design for all-purpose use.
- Tapered nose for easy working in confined areas.



D252-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)		
D252-6	6-1/8" (156 mm)	13/16" (21 mm)	3/4" (19 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.38		
Bell System Type "W" Notches – Slit insulation cleanly										
D252-6SW	6-1/8" (156 mm)	13/16" (21 mm)	3/4" (19 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.33		

## Standard Diagonal-Cutting Pliers -**Tapered Nose**

#### Additional Feature:

- Easy working in confined areas.
- Spring-loaded action for self-opening (Cat. No. D202-6C).



D202-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D202-6	6-1/8" (156 mm)	13/16" (21 mm)	11/16" (18 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.29
D202-6C	6-1/8" (156 mm)	13/16" (21 mm)	11/16" (18 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.31

## Standard Diagonal-Cutting Pliers - Tapered Nose

#### Additional Feature:

- Tapered nose for easy working in confined areas and close tip cutting.
- Spring-loaded action for self-opening (Cat. No. D245-5C).



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D245-5	5-1/16" (129 mm)	11/16" (18 mm)	9/16" (14 mm)	3/8" (10 mm)	standard	plastic-dipped	red	.20
D245-5C	5-1/16" (129 mm)	11/16" (18 mm)	9/16" (14 mm)	3/8" (10 mm)	standard	plastic-dipped	red	.20

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.





# **Diagonal-Cutting Pliers**

# Standard Diagonal-Cutting Pliers — Semi-Flush Cutting

#### Additional Features:

- Trims plastic or printed circuit boards.
- Spring-loaded for self-opening action.



D210-6C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D210-6C	6-1/8" (156 mm)	13/16" (21 mm)	11/16" (18 mm)	7/16" (11 mm)	semi-flush	plastic-dipped	red	.29

## Standard Diagonal-Cutting Pliers — Stripping Hole

#### Additional Features:

- Cleanly strips 16 AWG (1.0 mm) solid wire.
- Tapered nose for easy working in confined areas.



D240-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
D240-6	6-1/8" (156 mm)	13/16" (21 mm)	11/16" (18 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.30

# **Diagonal-Cutting Electronics Pliers**

## Diagonal-Cutting Pliers — Pointed Nose, Narrow Jaws

#### Additional Features:

- Narrow jaw and hinge for delicate work in tight areas.
- Sharp pointed nose for precise tip cutting.
- Spring-loaded action for self-opening.



D244-5C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D244-5C	5-1/16" (129 mm)	11/16" (18 mm)	1/2" (13 mm)	5/16" (8 mm)	flush	plastic-dipped	royal blue	.18

## **Midget Standard Diagonal-Cutting Pliers**

#### Additional Feature:

- Tapered nose for easy working in confined areas and close tip cutting.
- Spring-loaded action for self-opening (Cat. No. D257-4C).



D257-4C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D257-4	4-1/4" (108 mm)	1/2" (13 mm)	7/16" (11 mm)	1/4" (6 mm)	semi-flush	plastic-dipped	royal blue	.12
D257-4C	4-1/4" (108 mm)	1/2" (13 mm)	7/16" (11 mm)	1/4" (6 mm)	semi-flush	plastic-dipped	royal blue	.12

All dimensions are in inches and (millimeters).


**AWARNING:** Always wear approved eye protection.

# **Diagonal-Cutting Electronics Pliers**

#### Midget Diagonal-Cutting Pliers - Pointed Nose

#### Additional Features:

- Sharp pointed nose for precise tip cutting and trimming printed circuit boards.
- Spring-loaded for self-opening action.



D209-5C

#### Midget Diagonal-Cutting Pliers - Pointed Nose, Extra Narrow Jaws

#### Additional Features:

- Narrow jaw and hinge for delicate work in tight areas.
- Sharp pointed nose for precise tip cutting.
- Spring-loaded action for self-opening.

Cat. No.	Overall	Jaw	Jaw	Jaw	Cutting	Handle	Handle	Weight
	Length	Length	Width	Thickness	Knives	Finish	Color	(lbs.)
D259-4C	4-1/4" (108 mm)	1/2" (13 mm)	13/32" (10 mm)	1/4" (6 mm)	flush	plastic-dipped	royal blue	.12

D259-4C

## Midget Diagonal-Cutting Pliers - Tapered Nose, Midget Jaws

#### Additional Features:

- Miniature jaw for close-quarter work with maximum visibility.
- Sharp pointed nose for precise tip cutting.
- Spring-loaded action for self-opening.

Cat. No.	Overall	Jaw	Jaw	Jaw	Cutting	Handle	Handle	Weight
	Length	Length	Width	Thickness	Knives	Finish	Color	(lbs.)
D295-4C	4-1/4" (108 mm)	1/2" (13 mm)	3/8" (10 mm)	1/4" (6 mm)	flush	plastic-dipped	roval blue	.11

D295-4C

## Midget Diagonal-Cutting Pliers - Nickel Ribbon Wire Cutters

#### Additional Features:

- Designed to cut nickel ribbon wire.
- Nose tip is only 1/32" (0.8 mm) for precise work in confined areas.
- Cutting knife tip is 3/16" (5 mm) long for precise cutting.
- Spring-loaded action for self-opening.

Cat. No.	Overall	Jaw	Jaw	Jaw	Cutting	Handle	Handle	Weight
	Length	Length	Width	Thickness	Knives	Finish	Color	(lbs.)
D230-4C	4-1/4" (108 mm)	1/2" (13 mm)	7/16" (11 mm)	1/4" (6 mm)	semi-flush	plastic-dipped	royal blue	.12

D230-4C

## **Lightweight Flush Cutter**

#### Additional Features:

- Shears wire up to 18 AWG producing a flat, flush cut.
- Shear cutting greatly reduces cutting effort and minimizes fly-off.
- Cushioned grips and steel return spring for increased comfort during repetitive cutting.
- Ultra slim profile increases access in confined areas.
- Heat treated for increased durability.

D275-5

Cat. No.	Overall Length	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D275-5	5" (127 mm)	flush	plastic	red	.11

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# **Long-Nose Pliers**

#### Features:



#### **All-Purpose Pliers**

**JOURNEYMAN** 

#### Additional Features:

- Strips 8-16 AWG Solid and 10-18 AWG Stranded wire.
- Induction-hardened cutting knives for increased wire cutting performance, including hard wire.
- Long nose for grabbing and looping wire.
- 6-32 and 8-32 screw shearing.
- Dual material Journeyman<sup>™</sup> handles provide better grip.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	<b>Handle Color</b>	Weight (lbs.)
J206-8C	8-5/8" (214 mm)	2-3/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	1/2" (13 mm)	1/8" (3 mm)	Journeyman	yellow/gray	.60

## Heavy-Duty Long-Nose Pliers - Side-Cutting

#### Additional Features:

- Induction-hardened cutting knives for long life.
- · Heavier design for greater cutting power.
- Extended handles provide added reach and leverage.





D203-8NCR

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)	
D203-8	8-7/16" (214 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	plastic-dipped	yellow	.60	
Journeyman™ Series – Dual-material handles										
J203-8	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.63	
Wire Strip	ping – Cleanly stri	os 12 AWG wire								
D203-8N	8-7/16" (214 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	plastic-dipped	yellow	.59	
Journeym	an™ Series – Dual-	material handles	•							
J203-8N	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.64	
Wire Strip	ping & Crimping –	Cleanly strips 12	AWG wire; a	rimps connector	s, lugs & term	inals				
D203-8NCR	8-7/16" (214 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	plastic-dipped	yellow	.61	
Refer to the	e insulated section fo	r insulated pliers.								

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

# **Long-Nose Pliers**

## Standard Long-Nose Pliers - Side-Cutting

#### Additional Features:

- Induction-hardened, long-lasting cutting knives.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.
- Spring-loaded action for self-opening (Cat. Nos. D203-6C, D203-7C).



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)	
D203-6	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.27	
D203-6C	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.27	
D203-7	7-3/16" (183 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.29	
D203-7C	7-3/16" (183 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.29	
Journeyn	man™ Series – Dua	al-material hand	les							
J203-6	6-3/4" (171 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.30	
J203-7	7-5/16" (186 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.33	
Switchbo	oard Work – Clean	ly strips 19 & 22	? AWG wire							
D203-6H2	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.26	
Refer to ti	Refer to the insulated section for insulated pliers.									

## **Standard Long-Nose Pliers**

#### Additional Features:

- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.
- Spring-loaded action for self-opening (Cat. No. D301-6C).



D301-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D301-6	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	3/32" (2 mm)	plastic-dipped	yellow	.29
D301-6C	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	3/32" (2 mm)	plastic-dipped	vellow	.28

## **Long-Reach Long-Nose Pliers**

#### Additional Features:

- Long handles and nose allow greater access to confined, hard-to-reach areas.
- Long-reach design provides greater holding power at the tip with minimal effort.
- Mating surfaces and dimensions are precision machined for faultless tool performance.
- Pliers are hot riveted for uniformly smooth opening and closing action.
- Knurled jaws for precise gripping and sure wrapping and looping of wire.
- Custom US tool steel is forged, precision machined, hardened and tempered for maximum strength, exceptional performance, and long life.
- Plastic-dipped yellow handles are comfortable and easy to identify.
- Pliers are individually adjusted to meet performance standards far exceeding application requirements.
- 45° bent style reaches around obstructions (Cat. No. D362-11).



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



D362-11



# **Electronics Long-Nose Pliers**

## **Slim Long-Nose Pliers**

#### Additional Features:

- Longer nose and handles for deeper reach into work.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D307-5 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)		
Knurled Jaws – Sure-wrapping and looping										
D307-5 1/2C	5-5/8" (143 mm)	1-11/16" (43 mm)	1/2" (13 mm)	5/16" (8 mm)	1/32" (.8 mm)	plastic-dipped	yellow	.15		
Smooth Insi	Smooth Inside Jaws – Radiused jaw edges help prevent nicking wire									
D327-5 1/2C	5-5/8" (143 mm)	1-11/16" (43 mm)	1/2" (13 mm)	5/16" (8 mm)	1/16" (1.6 mm)	plastic-dipped	dark blue	.16		

## Midget Long-Nose Pliers - Slim-Nose

#### Additional Features:

- Lightweight, slim-nose pliers for precision subminiature assembly work.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.
- Spring-loaded action for self-opening.



D322-4 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)			
D321-4 1/2C	4-13/16" (122 mm)	1-1/16" (27 mm)	7/16" (11 mm)	1/4" (6 mm)	1/32 x 1/16" (.8 x 1.6 mm)	plastic-dipped	royal blue	.14			
Smooth Insid	Smooth Inside Jaws – Radiused jaw edges help prevent nicking wire										
D322-4 1/2C	4-13/16" (122 mm)	1-1/16" (27 mm)	7/16" (11 mm)	1/4" (6 mm)	1/32 x 1/16" (.8 x 1.6 mm)	plastic-dipped	royal blue	.14			

## **Midget Flat Long-Nose Pliers**

#### Additional Features:

- Jaw width tapers to narrow flat tip for sure gripping in confined areas.
- Polished inside jaws help prevent nicking wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D323-4 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D323-4 1/2C	4-13/16" (122 mm)	1-1/16" (27 mm)	7/16" (11 mm)	1/4" (6 mm)	1/8 x 1/16" (3 x 1.6 mm)	plastic-dipped	royal blue	.14

## **Tapered Long-Nose Pliers**

#### Additional Features:

- Larger and sturdier yet tapered design allows access into tight areas.
- Knurled jaws for sure wrapping and looping.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D310-6C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D310-6C	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/16" (1.6 mm)	plastic-dipped	yellow	.27

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

# **Electronics Long-Nose Pliers**

## Long-Nose Pliers - Chain Nose

#### Additional Features:

- Knurled jaws for sure gripping, bending and forming of medium-gauge wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



Cat No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D317-5C	5-1/16" (129 mm)	1-1/8" (29 mm)	1/2" (13 mm)	5/16" (8 mm)	1/16" (1.6 mm)	plastic-dipped	yellow	.14

## Needle-Nose Pliers - Side-Cutting

#### Additional Features:

- Extra length for added reach in confined areas.
- Knurled jaws for sure wrapping and looping.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D203-6SCPC	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	1/16" (1.6 mm)	plastic-dipped	yellow	.26

## **Long Needle-Nose Pliers**

#### Additional Features:

- Designed for accurate work in hard-to-reach areas.
- Knurled jaws for sure wrapping and looping.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D318-5 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)	
D318-5 1/2C	5-5/8" (143 mm)	1-11/16" (43 mm)	1/2" (13 mm)	5/16" (8 mm)	1/16" (1.6 mm)	plastic-dipped	yellow	.13	
Smooth Inside Jaws – Radiused jaw edges help prevent nicking wire edges									
D328-5 1/2C	5-5/8" (143 mm)	1-11/16" (43 mm)	1/2" (13 mm)	5/16" (8 mm)	1/16" (1.6 mm)	plastic-dipped	dark blue	.14	

## Long Needle-Nose Pliers - Extra-Slim

#### Additional Features:

- Long, narrow nose and slim hinge for extremely close quarter work.
- Finely knurled jaws grip thin wire without damaging it.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D335-5 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D335-5 1/2C	5-5/8" (143 mm)	1-11/16" (43 mm)	15/32" (12 mm)	1/4" (6 mm)	1/16" (1.6 mm)	plastic-dipped	royal blue	.13

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# **Electronics Long-Nose Pliers**

## **Curved Long-Nose Pliers**

#### Additional Features:

- 70° bent nose for maximum work visibility in confined areas.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.



D302-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D302-6	6-3/8" (162 mm)	1-1/2" (38 mm)	11/16" (18 mm)	3/8" (10 mm)	3/32" (2 mm)	plastic-dipped	yellow	.30

#### **Midget Curved Chain-Nose Pliers**

#### Additional Features:

- 60° bent nose for maximum work visibility in confined areas.
- Easily bends and forms fine wire.
- Polished inside jaws and radiused jaw edges prevent nicking wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D320-4 1/2C

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D320-4 1/2C	4-3/4" (121 mm)	1" (25 mm)	13/32" (10 mm)	1/4" (6 mm)	1/16" (1.6 mm)	plastic-dipped	royal blue	.13

# **Special Use Long-Nose Pliers**

## **Conduit Locknut and Reaming Pliers**

#### Additional Features:

- Tightens 1/2" and 3/4" EMT or 1/2" rigid locknuts.
- Fits liquid tight fittings and caps.
- Reams and smoothes both inside and outside of conduit.
- Knurled jaws at nose tip pull wire or fish tape.
- Machined nose fits snugly into locknut wings.








D333-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D333-8	7-3/4" (197 mm)	1-5/8" (41 mm)	15/16" (24 mm)	1/2" (13 mm)	3/16" (4.8 mm)	plastic-dipped	yellow	.55



**AWARNING:** Always wear approved eye protection.





# **Special Use Pliers**

## **End-Cutting Pliers**

- Wide throat clearance for clean, even cutting of wire or nails at close range.
- High-leverage design provides greater cutting power at the knives than other plier designs.
- Extended handles for longer reach and increased leverage.



D232-8

Cat.No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
D232-8	8-1/2" (216 mm)	3/8" (10 mm)	1-3/16" (30 mm)	19/32" (15 mm)	1-3/16" (30 mm)	plastic-dipped	red	.71

#### **Plastic Cutting Pliers**

- Precisely cuts injection mold sprues, gates and other plastic.
- Adjustable 1/16" hollow-head screw keeps knife-edges from damaging each other (not designed for use on metal).
- Spring-loaded for self-opening action.



D227-7C

Cat.No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
D227-7C	7-11/16" (195 mm)	1" (25 mm)	31/32" (25 mm)	1/2" (13 mm)	flush	plastic-dipped	red	.55

# **Slip-Joint Pliers**

#### **Slip-Joint Pliers**

- Shear-type cutter for precision wire cutting.
- Two versatile jaw positions.
- Serrated jaws provide sure-gripping power.
- Nickel-chrome plated for long life.



D511-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Handle Color	Weight (lbs.)
D511-6	6-9/16" (167 mm)	1-3/16" (30 mm)	1-3/16" (30 mm)	3/8" (10 mm)	plastic-dipped	blue	.39
D511-8	8-1/16" (205 mm)	1-3/8" (35 mm)	1-1/4" (32 mm)	7/16" (11 mm)	plastic-dipped	blue	.62
511-10	9-3/4" (248 mm)	1-3/4" (44 mm)	1-3/8" (35 mm)	15/32" (12 mm)	plain	n/a	.81
D511-10	9-7/8" (251 mm)	1-3/4" (44 mm)	1-3/8" (35 mm)	15/32" (12 mm)	plastic-dipped	blue	.83

## Slip-Joint Pliers – Hose Clamp

- Quickly installs and removes spring-tension hose clamps.
- Grips with either end or side of jaws for work in confined areas.
- Nickel-chrome plated for long life.



D514-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Handle Color	Weight (lbs.)
D514-8	8-1/16" (205 mm)	1-3/8" (35 mm)	1-1/4" (32 mm)	7/16" (11 mm)	plastic-dipped	blue	.61

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# **Pump Pliers**

#### Klaw™ Pump Pliers

- Push button and quick ratchet feature allows for fast and easy adjustment to any position. (Cat. Nos. D504-10B, D504-12B).
- Compact, narrow design for easy work in small or hard to reach spaces.
- Gripping surfaces with specially hardened teeth for reduced wear and positive gripping.
- Extended grips for added comfort.







#### **Quick-Adjust Pump Pliers:**

Push button and quick ratchet feature allows for fast and easy adjustment to any position. (Cat. Nos. D504-10B, D504-12B).

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight					
Quick-Adjust Klaw™ Pump Pliers										
D504-10B	10-1/8" (257 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	0.79 lbs. (0.36 kg)					
D504-12B	12-1/2" (318 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.2 lbs. (0.54 kg)					
Classic Klaw™ Pur	mp Pliers									
D504-7	7-3/8" (187 mm)	1-3/8" (35 mm)	plastic-dipped	yellow	0.34 lbs. (0.15 kg)					
D504-10	9-7/8" (250 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	0.81 lbs. (0.37 kg)					
D504-12	12" (305 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.4 lbs. (0.64 kg)					

#### **Pump Pliers**

- Secure tongue and groove design for non-slip grip – even with heavy pressure.
- · Wide range of versatile jaw positions.



D502-6

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight (lbs.)
D502-6	6-1/2" (165 mm)	7/8" (22 mm)	plastic-dipped	yellow	.41
D502-10	10" (254 mm)	1-3/4" (45 mm)	plastic-dipped	yellow	.97
D502-12	12-1/4" (311 mm)	2-3/8" (60 mm)	plastic-dipped	yellow	1.37
D502-16	16-3/4" (425 mm)	4-1/4" (108 mm)	plastic-dipped	yellow	3.22
Journeyman™ Series -	Dual-material handles				
J502-10	10-1/4" (260 mm)	1-3/4" (45 mm)	Journeyman	yellow/black	1.02

Refer to the insulated section for insulated pliers.

## Pipe-Wrench Pliers - Angled Head

- 90° angled jaws provide 20% more leverage than 32° angled jaws.
- Secure tongue and groove design for non-slip grip – even with heavy pressure.
- Seven versatile jaw positions.
- Handle stop design prevents pinched fingers.



Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight (lbs.)
D503-10	10-1/4" (260 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	1.14
D503-12	13-1/4" (336 mm)	2-5/8" (67 mm)	plastic-dipped	yellow	2.14

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# **Pliers Handles**

## Replacement Klein-Koat® Pliers Handles

• Plastic material for slip-resistant grip and comfort.

Cat. No.	Size to Fit Pliers	Color	Weight (lbs.)
60	6" (152 mm) long	maroon	.05
70	7" (178 mm) long	maroon	.10
89	8" - 9" (203 mm - 229 mm) long	maroon	.10





70

## **Replacement Comfort-Grip Pliers Handles**

- Klein exclusive slip-reducing pliers handle.
- Aerated plastic construction provides firm and resilient cushion.

Cat. No.	Size to Fit Pliers	Color	Weight (lbs.)
55	5" - 6-1/2" (127 mm - 165 mm) long	red	.05



55

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.







State-of-the-art dual material molding process



Contoured thumb area for additional comfort

and positive feel.

Soft material on outer surface for comfort and a firm grip.



#### **High-Leverage Side-Cutting Pliers**

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



J2000-9NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)	
J213-8NE	New England	8-13/16" (224 mm)	1-7/16" (37 mm)	1-3/16" (30 mm)	5/8" (16 mm)	23/32" (18 mm)	Journeyman	dark blue/black	.97	
J213-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.13	
2000 Series* – Heavy-duty cutting knives										
J2000-9NE	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.13	
*Cuts ACS	R screws nail	s and most harden	ed wire. Features co	mhination nolishe	d and black-oxide	finish				

Color-coded yellow, dark blue, red, or light blue

handles allow quick identification of tool.

#### High-Leverage Side-Cutting Pliers - Fish-Tape Pulling

#### Additional Features:

- Easily pulls 1/8" or 1/4" flat steel fish tape without damaging the tape.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J213-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.11
2000 Series	* – Heavy-dut	y cutting knives							
J2000-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.14
+0t- 400D			Luina Faatuusa san	alata aktawa wa altaba	al and black and de	E-1-1-			

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

## High-Leverage Side-Cutting Pliers — Connector Crimping

#### Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)		
J213-9NECR	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	yellow/black	1.13		
2000 Series* – Heavy-duty cutting knives											
J2000-9NECR*	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.12		
*Cuts ACSR, s	*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.										

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



## High-Leverage Side-Cutting Pliers -**Connector Crimping & Fish Tape Pulling**

#### Additional Features:

- Built-in crimper works on non-insulated connectors, lugs, and terminals.
- Built-in channel pulls steel fish tape without damaging the tape.
- 2000 series heavy-duty cutting knives cut ACSR, screws, nails, and most hardened wire.







J2000-9NECRTP

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2000-9NECRTP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.13

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

#### **High-Leverage Universal Combination Pliers**

#### Additional Features:

- Universal tapered head-design allows greater access in confined spaces.
- · Precision machined pipe-grip for greater gripping power.
- Crimping die behind hinge for superior leverage crimping of non-insulated connectors, lugs and terminals.



J12098

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J12098	Universal	8-3/4" (222 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	17/32" (13 mm)	3/4" (19 mm)	Journeyman	dark blue/black	.82

## 8" High-Leverage Side-Cutting Pliers

#### Additional Features:

- · High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power.
- 2000 series cut screws, nails, and most hardened wire.
- Combination polished and black-oxide finishes.



Weight	(lbs.)

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2000-8	New England Tapered	8-13/16" (224 mm)	1-7/16" (37 mm)	1-7/64" (28 mm)	5/8" (16 mm)	3/4" (19 mm)	Journeyman	light blue/black	.93

## 7" Side-Cutting Pliers

#### Additional Features:

- 2000 series cut screws, nails, and most hardened wire.
- Combination polished and black-oxide finishes.



J2001-7NE

Cat. No. Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
J2001-7NE New England	7-9/16" (192 mm)	1-9/32" (33 mm)	1-1/16" (27 mm)	1/2" (13 mm)	5/8" (16 mm)	Journeyman	light blue/black	.61

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

## **High-Leverage Diagonal-Cutting Pliers**

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.



J2000-28

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	<b>Cutting Knives</b>	Handle Finish	Handle Color	Weight (lbs.)
J228-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.67
2000 Serie	s* – Heavy-duty d	cutting knives						
J2000-28	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.67

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

#### High-Leverage Diagonal-Cutting Pliers - Angled Head

#### Additional Features:

- Angled head design for easy work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire.
- Induction-hardened cutting knives for long life.
- · Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
J248-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.61
2000 Seri	ies* – Heavy-duty c	utting knives						
J2000-48	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.61

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

# **Long-Nose Pliers**

#### **All-Purpose Pliers**

#### Additional Features:

- Strips 8-16 AWG Solid and 10-18 AWG Stranded wire.
- Induction-hardened cutting knives for increased wire cutting performance, including hard wire.
- Long nose for grabbing and looping wire.
- 6-32 and 8-32 screw shearing
- Dual material Journeyman<sup>™</sup> handles provide better grip.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D206-8C	8-5/8" (214 mm)	2-3/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	1/2" (13 mm)	1/8" (3 mm)	Journeyman	yellow/gray	.60

## Heavy-Duty Long-Nose Pliers - Side-Cutting

#### Additional Features:

- Induction-hardened, long-lasting cutting knives.
- Heavier design for greater cutting power.
- Slim head design for working in confined areas.
- Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)	
J203-8	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.63	
Wire Stri	Wire Stripping – Cleanly strips 12 AWG wire									
J203-8N	8-9/16" (218 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)	Journeyman	yellow/black	.64	

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# **Long-Nose Pliers**

#### **JOURNEYMAN**

#### **Standard Long-Nose Pliers**

#### Additional Features:

- Slim head design for working in confined areas.
- Induction-hardened, long-lasting cutting knives.
- Knurled jaws for sure wrapping and looping.
- Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
J203-6	6-3/4" (171 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.30
J203-7	7-5/16" (186 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.33

# **Pump Pliers**

#### **Pump Pliers**

#### Additional Features:

- Secure tongue and groove design for non-slip grip – even with heavy pressure.
- · Wide range of versatile jaw positions.
- Tension-loaded joint to reduce handle wobble for sure gripping.
- Induction-hardened jaws for long life.



J502-10

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight (lbs.)
J502-10	10-1/4" (260 mm)	1-3/4" (45 mm)	Journeyman	yellow/black	1.02

# **Crimping Tool**

## Crimping/Cutting Tool - Non-Insulated/Insulated Connectors

#### Additional Features:

- Designed to crimp insulated and non-insulated 10 to 22 AWG solderless terminals and connectors.
- Tapered nose design for working in confined spaces.
- Contoured thumb area for additional comfort and positive feel.
- Specially hardened cutter.
- Hot-riveted joint ensures smooth action and no handle wobble.



Cat. No.	Overall Length	Handle Finish	Handle Color	Weight (lbs.)
J1005	9-3/4" (248 mm)	Journeyman	red/black	.84

## **Cable Cutter**

## **High-Leverage Cable Cutter**

#### Additional Features:

- Cuts up to 4/0 aluminum AWG (no ACSR), 2/0 AWG soft copper and 100-pair 24 AWG communications cable.
- High-leverage for greater cutting power.

AWARNING: Do NOT use to cut steel or ACSR.

Precision, one-hand shearing action.



J63050

Cat. No.	Overall Length	Handle Finish	Handle Color	Weight (lbs.)
J63050	9-9/16" (243 mm)	Journeyman	red/black	.98


All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



28



# **Telecom Tools**

## **Bell-System Pliers Selection Chart**

Bell-System Designation	Cat. No.
Type B Long-Nose	D301-6
List 1 Long-Nose	71980
Type B Short-Nose	D2291
Diagonal B-5	D245-5

Bell-System Designation	Cat. No.
Diagonal B V-Notch	D528V
Diagonal D-6	72192
8" B Sidecut	D213-8NE
9" B Sidecut	D213-9NE

Bell-System Designation	Cat. No.
C Pressing	D234-6
C Pressing	VDV026-049
	220.0

## Diagonal Bell-System Pliers - "W" & "V" Notches

- "W" notches to cleanly slit insulation.
- "V" notch at the hinge for quick insulation crushing.
- Tapered nose for easy working in confined areas and close tip cutting.



D528V

Cat. No.	Overall	Jaw	Jaw	Jaw	Cutting	Handle	Handle	Weight
	Length	Length	Width	Thickness	Knives	Finish	Color	(lbs.)
D528V	5-3/16" (132 mm)	13/16" (21 mm)	9/16" (14 mm)	3/8" (10 mm)	standard	plastic-dipped	red	.20

## Diagonal Telephone Work Pliers - Type D-6

- Tapered nose for easy working in confined areas and close tip cutting.
- Convenient .030" and .045" stripping holes.
- "V" stripping notch in jaw for quick insulation slitting.
- Serrated behind the hinge to crush insulation.



72192

Cat. No.	Overall	Jaw	Jaw	Jaw	Cutting	Handle	Handle	Weight
	Length	Length	Width	Thickness	Knives	Finish	Color	(lbs.)
72192	6-1/8" (156 mm)	13/16" (21 mm)	3/4" (19 mm)	7/16" (11 mm)	standard	plastic-dipped	red	.33


## **Scotchlok® Connector Crimping Pliers**

- Crimps and seats UR, UY, and UG connectors.
- Curved handles for greater control.
- Induction-hardened side-cutting knives for long life.





D234-6



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight (lbs.)
D234-6	5-13/16" (148 mm)	1-3/32" (28 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	plastic-dipped	yellow	.25
D234-6C*	5-13/16" (148 mm)	1-3/32" (28 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	plastic-dipped	yellow	.25

<sup>\*</sup>Spring-loaded action for self-opening. Scotchlok® is a registered trademark of 3M.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.





## **Telecom Tools**

## **Connector Crimping Long-Nose Pliers**

- Crimps UR/UY/UG insulation displacement connectors (IDC) – Scotchlok® type connectors.
- Grooved jaws for wire wrapping, looping and twisting.
- Cleanly strips 23 AWG and 24 AWG wire.
- Hot-riveted joint ensures smooth action and no handle wobble.
- Induction-hardened cutting knives for long life.
- Yellow plastic grips enhance comfort, visibility and allow quick identification.



VDV026-049



Cat. No	Overall	Jaw	Jaw	Jaw	Knife	Point	Handle	Handle	Weight
	Length	Length	Width	Thickness	Length	Thickness	Finish	Color	(lbs.)
VDV026-049	6.8" (173 mm)	2" (51 mm)	0.70" (18 mm)	0.38" (10 mm)	0.44" (11mm)	0.095 x 0.125 (2.0 mm x 3.0 mm)	plastic-dipped	yellow	.28

Scotchlok® is a registered trademark of 3M Corporation.

## Long-Nose Telephone Work Pliers - Stripping

- Cleanly strips 22 (.34 mm<sup>2</sup>) to 24 (.25 mm<sup>2</sup>) AWG wire.
- · Convenient insulation crushing slot.
- Curved handles provide greater tool control.



D2291

Cat. No.	Overall	Jaw	Jaw	Jaw	Point	Handle	Handle	Weight
	Length	Length	Width	Thickness	Thickness	Finish	Color	(lbs.)
D2291	6" (152 mm)	1-1/4" (32 mm)	11/16" (18 mm)	3/8" (10 mm)	1/16" x 3/32" (1.6 mm x 2 mm)	plastic-dipped	yellow	.25

## Long-Nose Telephone Work Pliers - Type L1

- Knurled jaw tips for greater gripping power.
- Induction-hardened side-cutting knives for long life.
- Convenient .030" stripping hole.
- Curved handles provide greater tool control.





71980

Cat. No.	Туре	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
71980	L1	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	1/16" x 3/32" (1.6 mm x 2 mm)	plastidipped	yellow	.25

## Standard Long-Nose Pliers - Switchboard Work

- Cleanly strips 19 & 22 AWG wire.
- Induction-hardened, long-lasting cutting knives.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.





D203-6H2

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
D203-6H2	6-5/8" (168 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	plastic-dipped	yellow	.26

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



## **Telecom Tools**

#### **Can Wrench**



- Two tools in one: saves space in your pouch.
- One end opens telephone box fasteners. the other end tightens nuts on binding-post terminals.
- The 7/16" socket has a black finish and the 3/8" socket
- Sockets are 1-1/4" (32 mm) deep to fit over long binding posts and are thin-walled for easy access into tight areas.
- Socket ends are color-coded for quick identification of socket sizes.
- Hex-socket design enables using a wrench to obtain extra torque.
- High-impact, break-resistant handle for long and dependable service.
- Sockets are heat-treated, alloy steel.

Cat. No.	Description	Length	Handle Diameter	Weight
68005	3/8" and 7/16" hex nut	7" (178 mm)	1" (25 mm)	.35 lbs. (0.16 kg)

#### **Bell System Type Wrench**



3146B

1659-5AT

Serpentine Jaw

- Similar to standard lineman's wrench, but with end openings sized to NEMA hardware specifications.
- Silver painted finish.

Cat. No.	Description	Length	Weight
3146B	Large end has 1-1/16" and 1-3/16" openings. Small end has 11/16" and 7/8" openings.	13" (330 mm)	1.76 lbs. (0.80 kg)

AWARNING: NOT insulated. Will NOT protect against electrical shock.

# **Steel Strand Wire Pulling Grips**

## Bell System B, L, and H Chicago® Grips - 1628, 1659, 1684 & 1692 Series

- All are equipped with chain, toggle and shackle keeps the grip from falling off of cable.
- 1659 5AT is similar to Bell-System type "B" Strand Puller. Designed to pull 1/4" (6.35 mm) figure-8 telephone cable. Also has serpentine jaw.
- 1684 5AT is identical to Bell-System type "L" Strand Puller.
- 1628 16AT is identical to Bell-System type "H" Strand Puller.

Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each						
5,000 lbs. (2,268 kg) Ma	ximum Safe Load								
1659-5AT ("B" Strand Puller)	.20"37" (5.08 mm - 9.40 mm)	5" (127 mm)	6.7 lbs. (3.03 kg)						
8,000 lbs. (3,629 kg) Maximum Safe Load									
1684-5AT ("L" Strand Puller)	.218"550" (5.54 mm - 13.97 mm)	5" (127 mm)	6.9 lbs (3.13 kg)						
1692-5AT ("L" Strand Puller)	.218"550" (5.54 mm - 13.97 mm)	5" (127 mm)	6.6 lbs (3.00 kg)						
15,000 lbs. (6,803 kg) Maximum Safe Load									
1628-16AT ("H" Strand Puller)	.31"62" (7.87 mm - 15.75 mm)	7 1/4" (184 mm)	15.8 lbs (7.16 kg)						
*1692-5AT (larger clampin	g force than 1684-5AT)								

AWARNING: Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

AWARNING: Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

**AWARNING:** When used on/or near energized lines, ground,

**AWARNING:** Grips are to be used for temporary installation, not for

All dimensions are in inches and (millimeters).

insulate, or isolate grip before pulling.

permanent anchorage.

**AWARNING:** Always wear approved eye protection.









## Strippers

#### **Radial Stripper UTP/STP**

- One-step outer jacket stripping, 1-level, of category 3, 5, 5e, and 6 cables.
- Durable high-carbon steel cutting blades are ground and honed for long life.
- Removes the outer jacket of twisted pair cable without damaging the conductors.
- Strip and slit lengths may be varied to accommodate different connector requirements.
- Recessed cutting surface slits long runs of twisted-pair cable.
- Multiple nest cavities allow the removal of a wide variety of jacket materials on twisted-pair cable.
- Tension loop can be disengaged for thin-jacket cable.
- One-piece construction ensures alignment for precise stripping.
- Large finger loop promotes rotation during use.
- Adjustable set-screw prevents twisted-pair conductor insulation scoring.

Cat. No.	Color	Strips or Slits	Level(s)	Strip/Slit Dimensions	Prepared Cable	Overall Length	Weight
VDV120-006	yellow	unshielded twisted pair shielded twisted pair	1	strip length varies by application		4.4" (112 mm)	1.3 oz. (36.9 g)

## **Coax Combination Radial Stripper – 2-Level**

- Two stripping cavities: one for standard size cable and one for utility size cables.
- Cuts five different series of RG cable including: RG6, RG6-QS, RG59, RG11 and RG7.
- 2-level stripping in one step 5/16" and 1/4" (7.9 mm and 6.4 mm).
- Klein's exclusive sliding depth gauge pre-measures cable for fast, accurate and repeatable strips.
- Durable high-carbon steel cutting blades automatically adjust to different cable diameters.
- Finger loop facilitates easy, controlled rotation.
- Easy debris clean-out.
- Perfect for the data installer who works with utility cable as well standard cable.

Cat. No.	Color	Levels	Strip Dimensions	Prepared Cable	Overall Length	Weight (oz)
VDV110-095	yellow/gray	2	5/16" and 1/4" (7.9 mm and 6.4 mm)		5.25" (133 mm)	1.5 oz. (42.5 g)

## **Coax Cable Radial Stripper – 2-Level**

- 2-level stripping in one step 5/16" and 1/4" (7.9 mm and 6.4 mm).
- Klein's exclusive sliding depth gauge pre-measures cable for fast, accurate and repeatable strips.
- Durable high-carbon steel cutting blades automatically adjust to different cable diameters.
- Finger loop facilitates easy, controlled rotation.



VDV110-061

Cat. No.	Color	Levels	Strip Dimensions	Prepared Cable	Overall Length	Weight (oz)
VDV110-061	yellow/black	2	5/16" and 1/4" (7.9 mm and 6.4 mm)		4.6" (116 mm)	1.2 oz. (34.0 g)

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits




VDV120-006

VDV110-095

# **Radial Strippers and Cartridges**

## **Radial Cartridge Strippers**

- Designed for high-volume, multiple-type cable preparation environments.
- Includes storage cartridge-bay.
- One-piece construction ensures precise stripping and never requires adjustment.
- Large finger loop promotes rotation during use.
- Cartridges snap in from both sides for left or right-handed operation.
- F-Connector "nest" assists with cable insertion.
- Durable high-carbon steel cartridge cutting blades are ground and honed for long life.
- Replacement cartridges available.



VDV110-802

Cat. No.	Set Contains					Overall Length	Weight
VDV100-801						5.6" (143 mm)	2.4 oz. (68.0 g)
	Cat. No.	Description	Color	Level(s)	Strip Dimensions	Prepared Cal	ile
	VDV100-001	dual cartridge radial stripper frame	yellow	-			
	VDV110-003	RG59/RG6/RG6-QS coaxial cable	black	2	5/16" and 1/4"(7.9 mm and 6.4 mm)	-	$\supset$
	VDV120-005	UTP cable	blue	1	variable		$\supset$
VDV110-802						5.2" (133 mm)	2.1 oz. (59.5 g)
	VDV100-002	radial cartridge stripper frame	yellow	-			
	VDV110-003	RG59/RG6/RG6-QS coaxial cable	black	2	5/16" and 1/4"(7.9 mm and 6.4 mm)		$\supset$

#### **Radial Stripper Cartridges**

#### Designed for use with:

Dual Cartridge Radial Stripper (Cat. No. VDV100-801)
Dual Cartridge Radial Stripper Frame (Cat. No. VDV100-001)
Radial Cartridge Stripper (Cat. Nos. VDV110-802 & VDV113-804)
Radial Cartridge Stripper Frame (Cat. No. VDV100-002)



- Durable high-carbon steel cutting blades are ground and honed for long life.
- Patented "V" notch eliminates scoring of the center conductor.\*
- Color coded for easy identification.
- Meets industry standards established by the SCTE (Society of Cable Telecommunication Engineers).
- Cartridges made from glass filled polycarbonate for superior strength and extended durability.



VDV110-003

lii.



VDV440

VDV110-004

VDV110-020







VDV113-022

VDV113-021

VDV120-005

\*All cartridges except for VDV120-005.

Cat No.	Cable	Color	Level	Cartridge Strip Dimensions	Cable Illustration	Weight
VDV110-003	RG59/RG6/RG6 QS coaxial cable	black	2	5/16" x 1/4" (7.9 mm x 6.4 mm)		0.1 oz. (2.8 g)
VDV110-004	RG7/RG11 coaxial cable	gray	2	5/16" x 1/4" (7.9 mm x 6.4 mm)		0.1 oz. (2.8 g)
VDV120-005	UTP cable(category 3, 5, 5e and 6)	blue	1	variable		0.1 oz. (2.8 g)
VDV110-020	mini-coaxial cable	green	2	1/4" x 1/4" (6.4 mm x 6.4 mm)		0.1 oz. (2.8 g)
VDV113-021	RG58/RG59/RG62 coaxial cable	green	3	0.235" x 0.235" x variable (6 mm x 6 mm x variable)		0.1 oz. (2.8 g)
VDV113-022	RG58/RG59/RG62 coaxial cable	brown	3	0.109" x 0.312" x variable(2.8 mm x 7.9 mm x variable)	<b>—</b>	0.1 oz. (2.8 g)

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits





# **Coax Cable Tools**

#### Coaxial Cable Cutter - CCS

- Multi-functional blade for cutting copper-clad steel (CCS) coaxial cables and cutting and trimming data cables and other general cable/wire.
- Notched blade section optimized to cut common CCS coaxial cables such as RG-59, RG-6/6Q and RG-11.
- Shears blade section designed to cut and snip solid and stranded copper, aluminum, UTP/STP twisted pair wires and cables.
- Blade geometry ensures CCS coaxial cable retains shape when cut to facilitate easy insertion into connectors and excellent terminations.
- High-leverage design for genuine one-handed operation.
- Forged from custom, US-made steel and through- hardened to withstand steel cable cutting.



Cat. No.	Overall Length	Cutting Knives	Cuts	Handle	Handle Color	Weight
VDV600-096	7-5/8" (194 mm)	Custom notch for CCS coaxial cable	RG59 RG6	plastic-dipped	yellow	.60 lbs. (272 g)
		Standard shears for general purpose	RG6Q RG11			



#### Cushion-Grip F-Connector Insertion/ Extraction Tool





- 5" long shaft with 7/16" socket extends reach for connecting/removing F-connectors.
- 3/8"-32 threaded end holds standard F-Connectors for cable insertion.
- Cushion-Grip handle for greater torque and enhanced comfort.
- Precision machined high-carbon steel is hardened for long life.
- Durable chrome finish resists corrosion and extends tool life.

VDV312-012

Cat. No.	Color	Shank Tip	Handle Tip	Shank Length	Finish	Overall Length	Weight
VDV312-012	yellow/black	7/16" open socket	3/8"-32 threaded male F-connector	5" (127 mm)	chrome-plated	8.8" (222 mm)	7.5 oz. (212.6 g)



All dimensions are in inches and (millimeters).

**AWARNING:** Read carefully and understand instructions before using this tool.

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

# **Coax Connector Crimp Tools**

#### Compression Crimper – Lateral, Multi Connector

- One tool crimps most connectors to most coaxial cables Minicoax, RG58, RG59, RG62, RG6, RG6QS, RG7, and RG11.
- Unique cable selection wheel eliminates the need to change plunger tips, saving time and not losing parts.
- Heavy-duty zinc die-cast chassis for durable, long lasting performance.
- Open design with 180° capture mechanism provides easy insertion, complete compression and simple removal.
- F/BNC/RCA connector markings for quick adjustments.
- Integrated handle lock for easy storage.
- Spring loaded return increases user comfort and ease of use.
- Yellow and black contoured grips enhance comfort, visibility and allow quick identification.



VDV211-063



Connector markings for quick adjustments.

Cat. No	Color	Туре	Cable	Connectors	Overall Length	Weight
VDV211-063	yellow/black	compression crimper	coaxial	BNC F RCA	6.25" (158 mm)	18.5 oz. (524.5 g)

#### Compression Crimper - Compact, Multi-Connector

- Fast, reliable multiple-type compression connector installations.
- Crimps compression BNC, F and RCA connectors to coaxial cable.
- Adjustable universal plunger ensures accurate crimps on multiple types of connectors.
- Open design with 180° capture mechanism provides easy insertion, complete compression and simple removal of cable and connector.
- F/BNC/RCA connector markings for quick adjustments.
- Compact tool with integrated handle lock for easy storage.
- Spring loaded return increases user comfort and ease of use.
- Yellow contoured grips enhance comfort, visibility and allow quick identification.
- Steel body with chrome finish resists corrosion and extends tool life.



VDV211-048



Connector markings for quick adjustments.

Cat. No	Color	Туре	Cable	Connectors	Overall Length	Weight
VDV211-048	yellow/chrome	compression crimper	coaxial	BNC. F. RCA	5.6" (142 mm)	8.0 oz. (226.8 g)

#### Compact, F-Connector

- Fast, reliable F-Connector installation tool.
- Steel body with black-oxide finish for corrosion resistance and durability.
- Fixed plunger allows quick, easy insertion and removal of cable and connector.
- Fixed plunger accepts many common F-connector compression fittings.
- Compact tool with integrated handle lock.
- Yellow and black grips enhance comfort, visibility and allow quick identification.
- Spring loaded return increases user comfort and ease of use.



VDV212-008

Cat. No.	Color	Туре	Cable	Connectors	Overall Length	Weight
VDV212-008	yellow/black	compression crimper	coaxial	common F connectors	5.6" (142 mm)	9.8 oz. (277.8 g)

All dimensions are in inches and (millimeters).

**AWARNING:** Read carefully and understand instructions before using this tool.

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits



# All-inclusive tool cuts, strips and crimps voice and data cables.

# **Twisted Pair Crimp/Strip Tools**

- **Compact Ratcheting Modular Crimper**
- Cuts and strips CAT6, CAT5e, CAT3 and flat-satin voice cables.
- Crimps 6 and 8 position modular connectors.
- Heavy-duty ratchet ensures complete termination.
- Direct lateral crimp action provides more even, precise contact termination across all pins than ordinary indirect crimp tools.
- Compact, ergonomic design for easy usage and storage.
- 40% smaller than many other crimpers.
- · Quick reference connector wiring diagrams provided on the tool and downloadable to your mobile device.



VDV226-107

Cat. No.	Color	Cuts & Strips	Crimps Connectors	Position/Pair/ Conductors	Overall Length	Weight
VDV226-107	yellow/black	round STP/UTP data cable flat-satin phone cable 28-22 AWG (0.08 – 0.34 mm²)	RJ11, RJ12 and RJ45	6-position, 2-pair/4-conductor 6-position, 3-pair/6-conductor 8-position, 4-pair/8-conductor	5.25" (133 mm)	11.2 oz. (318 g)

#### **Ratcheting Modular Crimper/Stripper**

- Fast, reliable modular-crimp connector installation for voice and data applications.
- All-In-One Tool, cuts, strips and crimps paired-conductor cables (round STP/UTP and flat-satin phone cable).
- Crimps 4, 6, and 8 position modular connectors (RJ22, RJ11/RJ12 and RJ45).
- · Crimping dies are precision ground from high-carbon steel.
- Designed for Western Electric (WE)/Stewart Stamping (SS)-type modular connectors.
- Ratchet safety-release and a blade-guard on cutting and stripping knives reduce risk of injury.
- Full-cycle ratchet mechanism prevents the release of the connector prior to full compression.
- Yellow and black grips enhance comfort, visibility, and allow quick identification.
- Not for use with AMP<sup>®</sup> connectors.
- Replacement blade set available (Cat. No. VDV999-064).


AMP® is a registered trademark of TYCO, Inc.

VDV226-011

Cat. No.	Color	Cuts & Strips	Crimps Connectors	Position/Pair/ Conductors	Overall Length	Weight
VDV226-011	yellow/black	round STP/UTP, flat satin phone cable 22-28 AWG (0.08 - 0.34 mm²)	RJ11, RJ12 RJ22 and RJ45	4-position, 1-pair/2-conductor 4-position, 2-pair/4-conductor 6-position, 2-pair/4-conductor 6-position, 3-pair/6-conductor 8-position, 4-pair/8-conductor	7.5" (191 mm)	11.3 oz. (320.3 g)

# **Connector Crimping Long-Nose Pliers**

- Crimps UR/UY/UG insulation displacement connectors (IDC) - Scotchlok® type connectors.
- Grooved jaws for wire wrapping, looping and twisting.
- Cleanly strips 23 AWG and 24 AWG wire.
- Hot-riveted joint ensures smooth action and no handle wobble.
- Induction hardened cutting knives for long life.
- Yellow plastic grips enhance comfort, visibility and allow quick identification.



Scotchlok® is a registered trademark of 3M Corporation.

Cat. No	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight
VDV026-049	6.80" (173 mm)	2" (51 mm)	0.70" (18 mm)	0.38" (10 mm)	0.44" (11 mm)	0.095 x 0.125 (2.0 mm x 3.0 mm)	plastic-dipped	yellow	4.5 oz. (127.6 g)

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits



# **Punchdown Tools & Accessories**

#### **Punchdown Screwdriver Multi-Tool**

- Terminate and cut wire in one step with included 110/66 combination cut-type punchdown blade with precision ground cutting edge.
- Non-impact wire termination.
- Machine-tooled steel bits for superior strength.
- Heavy-duty blade barrel provides storage for bits.
- Bayonet-style (twist & lock) socket accepts most manufacturers' punchdown blades.
- Cushion-Grip handle for greater torque and enhanced comfort.
- Tip-Ident<sup>®</sup> for quick identification of tool.
- Two Phillips screwdriver tips: #1 and #2.
- Two slotted screwdriver tips: 3/16" and 1/4".
- Two nut drivers: 1/4" and 3/8".
- One hex key: 3/8".
- 6 pc. counter display available (Cat. No. VDV001-0816).





VDV001-081



Cat. No.	Color	Included Bits	Finish	Overall Length	Weight
VDV001-081	yellow/black	#1 & #2 Phillips, 3/16" & 1/4" Slotted, 66/110 Terminate & Cut 1/4" & 3/8" Nut Driver, 3/8" Hex-Key	chrome	8" (203 mm)	9.4 oz. (266.5 g)

#### **Cushion-Grip Impact Punchdown Tools — 110/66**

- Extra-long punch collar to reach into crowded blocks.
- Cushion-Grip handle for superior comfort.
- Hi / Lo impact settings for use on both 110 and 66 blocks as well as jacks.
- Dura-Blade™ 110/66 Cut Combination Punchdown Blade is designed for durability and performance.
- Professional pick/probe/spudger for precise maintenance of wires on blocks or jacks.
- Multi-pocket pouch with belt clip and reinforced bottom to prevent punctures.







	<b>'</b> ≪0
- 1	EST. 1857
- 1	
	\20018
	CODE

Cat. No.	Description			Overall Length	Weight
VDV427-822	cushion-grip impact punchdown tool kit – 110/66			9.125" (232 mm)	14.9 oz. (422 g)
Kit Contains		End 1 Configeration	End 2 Configeration		
VDV427-821*	cushion-grip impact punchdown tool with Dura-Blade™	110 terminate & cut	66 terminate & cut		
VDV327-103*	wire pick	hook	spudger	*Items also so	ld separately
kit exclusive	multi-pocket pouch with reinforced puncture-resistant bottom	-			

#### Replacement Blade

Cat. No.	Description	End 1 Configeration	End 2 Configeration	Overall Length	Weight
VDV427-104	Dura-Blade™ 110/66 cut combination punchdown blade	110 terminate & cut	66 terminate & cut	2.25" (57 mm)	.05 oz. (14 g)

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

**AWARNING:** Do NOT use to pry or chisel.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

# Voice/Dat Testers {



# **Punchdown Tools & Accessories**

#### **Punchdown Multi-Tool with 1110/66 Blade**

- Patent pending locking impact mechanism allows non-impact operation and sure driving with a variety of optional WorkEnds<sup>™</sup> driver bits.
- Terminate and cut wire in one step with included precision ground combination 66 & 110 blade.
- Integrated Hook and Spudger for fast, easy manipulation of wire and small components.
- Selectable (Hi/Low) impact-force settings meet industry standards.
- Spring loaded for fast, low effort seating and terminating.
- Dual material contoured chassis provides greater control and enhances comfort.
- Blade storage compartment with spring loaded locking mechanism.
- Color coded yellow on the cut side of the tool.
- Hook and Spudger neatly and compactly store in the chassis, out of the way when not in use.
- Induction hardened high-carbon steel for durability and long life.
- Cat. No, VDV427-807 Includes WorkEnds™ Kit with WorkEnds™ adapter, reach extension, and 4 driver bits (#1 and #2 Phillips and 3/16" and 1/4" Slotted) in a convenient carrier.
- Replacement blades/accessories available.









Cat. No	Set Contains					Overall Length	Weight
VDV427-806	punchdown mu	lti-tool with 110/66 b	olade			7.0" (176 mm)	5.6 oz. (159 g)
	Cat. No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2		
	VDV427-047	yellow/red/black	punchdown multi-tool chassis	_	_		
	VDV427-017	black	punchdown tool blade - combination 66/110 cut type	110 terminate & cut	66 terminate & cut		
						_	
VDV427-807	punchdown mu	lti-tool with 110/66 b	olade & WorkEnds™			7.88" (200 mm)	7.5 oz. (213 g)
	Cat. No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2		
	VDV427-047	yellow/red/black	punchdown multi-tool chassis	-	-		
	VDV427-017	black	punchdown tool blade - combination 66/110 cut type	110 terminate & cut	66 terminate & cut	_	
	VDV770-050	-	WorkEnds™ kit	-	-	_	

#### **Impact Punchdown Tools**

- Terminate cable in variety of cross-connect panels, blocks and keystone jacks.
- Spring loaded for fast, low effort seating and terminating.
- Selectable (Hi/Low) impact-force settings meet industry standards.
- Rubber finger grips and boot provide greater control and enhanced comfort.
- Blade storage compartment with spring loaded locking mechanism.
- Bayonet style (twist & lock) socket accepts most manufacturers' tools and blades.
- Induction-hardened high-carbon steel for durability and long life.
- Replacement blades available.





VDV427-800

Cat. No.	Set Contains:					Overall Length	Weight
VDV427-800	Impact Punchdov	ın Tool - Combinat	ion 66/110 Cut Type			7.0" (177 mm)	5.7 oz. (162 g)
	Cat No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2		
	VDV427-013	yellow/black	impact punchdown tool	-	-	_	
	VDV427-017	black	punchdown tool blade - combination 66/110 cut type	66 terminate & cut	110 terminate & cut	_	
VDV427-805	Impact Punchdow	/n Tool - 110 Type				7.1" (180 mm)	5.6 oz. (159 g)
	Cat No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2		
	VDV427-013	yellow/black	impact punchdown tool	-	-	_	
	VDV427-015	black	punchdown tool blade - 110 type	110 terminate	110 terminate & cut	_	

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

# **Punchdown Tools & Accessories**

#### Dura-Blade™ 110/66 Cut Combination Punchdown Blade

- Dura-Blade™ manufactured using Metal Injection Molding (MIM) technology for increased quality, durability and performance.
- Precise cutting-edge for clean, accurate wire insertion and trimming.
- Dual 110 and 66 cutting ends for versatility.
- Compatible with Klein<sup>®</sup> punchdown tools and other bayonet style (twist & lock) socket punchdown tools.





VDV427-104

Cat. No.	Color	Description	End 1 Configuration	End 2 Configuration	Overall Length	Weight
VDV427-104	chrome	Dura-Blade™ 110/66 Cut Combination Punchdown Blade	66 terminate & cut	110 terminate & cut	2.25" (57 mm)	.5 oz. (14 g)

#### **Punchdown Tool Blades & Accessories**

- Compatible with Klein® punchdown tools and other bayonet style (twist & lock) socket punchdown tools.
- Precision ground cutting-edge for clean, precise wire termination (depending on blade type).
- Terminate, and adjust cable in variety of cross-connect panels, blocks and keystone jacks.
- Induction-hardened high-carbon steel blades for durability and long life.
- Reversible blades with termination/cutting ends and termination only ends (depending on blade type).
- WorkEnds™ Kit converts the Punchdown Multi-Tool chassis (VDV427-047) into a multi-bit driver.
- Professional pick/probe/spudger for precise maintenance of wires on blocks or jacks.



VDV427-015



VDV427-016



VDV427-017







VDV770-050<sup>†</sup>



VDV327-103

Cat. No.	Color	Description	End 1 Configuration	End 2 Configuration	Overall Length	Weight
VDV327-103	yellow	wire pick	hook	spudger	7.25" (184 mm)	.1 oz. (3 g)
VDV427-015	black	high-carbon steel punchdown tool blade – 110 type	110 terminate	110 terminate & cut	2.1" (52 mm)	0.5 oz. (14 g)
VDV427-016	black	high-carbon steel punchdown tool blade – 66 type	66 terminate	66 terminate & cut	2.3" (58 mm)	0.6 oz. (17 g)
VDV427-017	black	punchdown tool blade – combination 66/110 cut type	66 terminate & cut	110 terminate & cut	2.2" (56 mm)	0.6 oz. (17 g)
VDV770-050	-	WorkEnds™ adapter, reach extension, and 4 driver bits (#1 and #2 Phillips and 3/16" and 1/4" Slotted) in a convenient carrier <sup>†</sup>	proprietary magnetic hex	1/4" female hex	3.2" (81 mm)	1.4 oz. (40 g)

<sup>&</sup>lt;sup>†</sup>WorkEnds™ is not compatible with VDV427-013, VDV427-800, VDV427-805.

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits



# **Crimp Tool and Die Sets**

#### **Ratcheting Crimper Frame**




VDV200-010

- Professional CATV, Electrical, Home Theater, Satellite and Security System ratcheting crimper frame with optional dies is perfect for fast, reliable connector installations.
- Full-cycle ratchet action assures a complete, precise crimp every cycle.
- Preset tension for optimum performance.
- Ratchet mechanism is designed to prevent the release of the connector prior to full compression.
- Safety crimp release helps eliminate rejected terminations due to incorrect positioning.
- Steel body with black-oxide finish for corrosion resistance and durability.
- Yellow and black grips enhance comfort, visibility, and allow quick identification.
- Thumb-screws secure die-sets for quick, easy changes.
- Optional, quick interchangeable die sets thumb and Phillips screw set available (see table).

Cat. No.	Overall Length	Weight
VDV200-010	8.75" (222 mm)	19.0 oz. (539 g)

#### **Coaxial Hex-Crimp Die Sets**

Cat. No	Die Set:	Nest Dimensions:	
VDV999-033	Replacement Screw Set (Thumb and Phillips)	N/A	111
VDV212-034	CATV F Connectors RG59/6	0.255"/0.320"/0.350" 6.48/8.13/8.89 mm	
VDV205-035	Insulated Terminals, AWG 10-22	AWG 22-18/16-14/12-10 DIN 0.5-1.0/1.5-2.5/4-6 mm <sup>2</sup>	
VDV205-036	Non-Insulated Terminal or Open Barrel Terminal, AWG 10-20	AWG 20-18/16-14/12-10 DIN 0.5-1/1.5-2.5/4-6 mm <sup>2</sup>	v vv
VDV211-037	RG6/58/59/62	0.256"/0.319"/0.068"/0.213" 6.50/8.10/1.73/5.41 mm	
VDV211-038	RG58/59/62	0.256 <sup>7</sup> /0.068 <sup>8</sup> /0.213 <sup>4</sup> 6.50/1.73/5.41 mm	
VDV205-039	Pin Terminal Insulated or Non- Insulated Ferrules, AWG 12-22	AWG 22/20/18/16/14/12 DIN 0.5/0.75/1.0/ 1.5/2.5/4 mm <sup>2</sup>	
VDV201-040	RG58/59/62/174 Fiber Optic	0.043"/0.068"/0.100"/ 0.137"/0.213"/0.255" 1.09/1.73/2.54/3.48/ 5.41/6.48 mm	
VDV211-041	RG58/59/62/6	0.255"/0.213"/0.098"/ 0.068"/0.321" 6.48/5.41/2.49/ 1.73/8.15 mm	
VDV201-042	RG174/179/Belden 8218 and Fiber Optic	0.042"/0.068"/0.078"/ 0.128"/0.151"/0.178" 1.07/7.73/1.98/3.25/ 3.84/4.52 mm	
VDV211-043	RG8/11/174/179/213	0.100"/0.128"/0.429" 2.54/3.25/10.90 mm	
VDV205-044	Non-Insulated Terminal, AWG 8-18	AWG 18-16/14/12-10/8 DIN 0.75-1.5/2.54/4- 6/10 mm <sup>2</sup>	



**AWARNING:** Read carefully and understand instructions before using this tool.

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Use cation when tightening thumb-screws to prevent thread damage/stripping and hand tighten only; do not over-tighten the thumb screws. Over-tightening thumb-screws can damage the tool and/or die set.







			Univ	ersal			Standard
Connector Type	F-Con	inector	BNC-Co	onnector	RCA-C	onnector	F-Connector
Crimping Type	Compr	ression	Compr	ression	Comp	ression	Compression
Cable Type:							
RG59	•		•		•		
RG6		•		•		•	•
RG6 QUAD SHIELD		•		•		•	
Universal Sleeve	•	•	•	•	•	•	
Outdoor Use							•
Cat. Nos:							
Pack Size: 10	VDV812-615	VDV812-606	VDV813-616	VDV813-607	VDV813-617	VDV813-608	VDV812-623
Pack Size: 35			VDV813-619	VDV813-613	VDV813-620	VDV813-614	
Pack Size: 50	VDV812-618	VDV812-612					VDV812-624
Klein Crimping Tools		VDV211-063, VDV211-048, VDV211-007				VDV211-063, VDV211-048, VDV211-007, VDV212-008	

#### **Universal Compression Connectors**

- Fit all manufacturers' diameter variations within a cable series.
- Fit difficult to work with multi-shield and plenum cables.
- For indoor use only.

Cat. No.	Connector Type	Cable Type	Pack Qty.
VDV812-615	F-Connector	RG59	10
VDV812-618	F-Connector	RG59	50
VDV812-606	F-Connector	RG6 - RG6Q	10
VDV812-612	F-Connector	RG6 - RG6Q	50
VDV813-616	BNC Connector	RG59	10
VDV813-619	BNC Connector	RG59	35
VDV813-607	BNC Connector	RG6 - RG6Q	10
VDV813-613	BNC Connector	RG6 - RG6Q	35
VDV813-617	RCA Connector	RG59	10
VDV813-620	RCA Connector	RG59	35
VDV813-608	RCA Connector	RG6 - RG6Q	10
VDV813-614	RCA Connector	RG6 - RG6Q	35

#### F • RG6-RG60





VDV812-606

VDV813-607

**BNC** • **RG59** 

VDV813-608





RCA • RG59

VDV812-615

VDV813-616

VDV813-617

#### **Standard Compression Connectors**

- Full ferrule design.
- Solid brass construction with nickel-plated finish.
- Best choice for outdoors.
- Great for satellite dishes.



VDV812-623

Cat. No.	Connector Type	Crimping Type	Cable Type	Pack Qty.
VDV812-623	F-Connector	Compression	RG6	10
VDV812-624	F-Connector	Compression	RG6	50

#### **Push-On Connectors**

- Patented, tool-less, easy grip design.
- Fits most major brands.
- For indoor use only.



VDV812-626

Cat. No.	Connector Type	Crimping Type	Cable Type	Pack Qty.
VDV812-625	F-Connector	Push-On	RG59	4
VDV812-626	F-Connector	Push-On	RG6 - RG6Q	4
VDV812-627	F-Connector	Push-On	RG6 - RG6Q	10





# **Adapters/Terminator**

#### F to BNC Adapter

#### Converts F-connectors to BNC connectors.



Cat. No.

VDV814-629

VDV814-630

VDV814-629

Description

F to BNC Adapter

F to RCA Adapter

#### F to RCA Adapter

Converts F-connectors to RCA connectors.



VDV814-630

#### F-Splice Adapter 3 GHz

Patented gripping mechanism for optimal signal strength.



VDV814-609

F-Terminator

# 90° F-Adapter 3 GHz

 Perfect for tight spaces in a cabinet or against a wall.



VDV814-631

Pack Qty.
2
2

Prevents extraneous signals from decreasing system performance.



VDV814-610

#### VDV814-609 F-Splice Adapter - 3 GHz 10 VDV814-631 90° F-Adapter - 3 GHz 2 VDV814-610 F-Terminator 10

# **Splitters/Diplexer**

- Over 130 dB of RFI shielding for optimal signal performance.
- Enhanced return path for improved cable modem performance.
- High return loss to minimize ghosting or pixelated images.
- F-terminators recommended for unused ports to optimize performance.

#### Digital Cable Splitters (5 MHz to 1 GHz)







VDV814-634



VDV814-635

Cat. No.	Description	Pack Qty.
VDV814-633	2-Way Digital Cable Splitter – 5 MHz - 1 GHz	1
VDV814-634	4-Way Digital Cable Splitter – 5 MHz - 1 GHz	1
VDV814-635	8-Way Digital Cable Splitter – 5 MHz - 1 GHz	1

#### **Satellite / Digital Cable Splitters** (5 MHz to 2.3 GHz)

• High port to port isolation to reduce interference.







VDV814-637

Cat. No.	Description	Pack Qty.
VDV814-636	2-Way Satellite/Digital Cable Splitter – 5 MHz - 2.3 GHz	1
VDV814-637	4-Way Satellite/Digital Cable Splitter – 5 MHz - 2.3 GHz	1

#### **Diplexer**

Combines or separates CATV and off-air signals with/from satellite signals.



VDV814-638

Cat. No.	Description	Pack Qty.
VDV814-638	Satellite/TV Diplexer – 5 MHz - 2.3 GHz	1

# **Twisted Pair Connectors**



Klein's data and telephone plugs are professional-grade and deliver consistent, reliable performance.

They feature thick 50 micro-inch gold plating on the contact plates, three-pronged solid and stranded wire contacts, and durable connector housings. Expect a sure connection each and every time.



Connector Type	UY	UR	RJ11	RJ11	R	J45
Position & Contacts	2P2C	3P3C	6P4C	6P6C	8P	980
Connector Design	1-Piece	1-Piece	1-Piece	1-Piece	1-Piece	3-Piece
Gold Plating Thickness (microinch)			50μ"	50μ"	50μ"	50μ"
Cable Type:						
CAT 3	•	•	•	•		
CAT 5					•	
CAT 5e					•	
CAT 6						•
Solid Conductor Wire	•	•	•	•	•	•
Stranded Conductor Wire					•	•
Connector Color	Yellow	Red	Clear	Clear	Clear	Clear
Cat. No.						
Pack Size: 10					VDV826-628	
Pack Size: 25	VDV826-604	VDV826-605	VDV826-601	VDV826-600		VDV826-603
Pack Size: 50					VDV826-602	
Pack Size: 100					VDV826-611	
Crimping Type IDC		OC .	Modular Plug Connector			
Klein Crimping Tools	D234-6, D234-6	6C, VDV026-049	VDV226-011, VDV226-107			

#### **RJ45 Modular Data Plugs**

- 8 position 8 contact.
- For solid or stranded conductors.



VDV826-628 (CAT 5 / CAT 5e)



VDV826-603 (CAT 6)

Cat. No.	Connector Type	Cable Type	Connector Color	Pack Qty.
VDV826-628	RJ45	CAT 5 / CAT 5e	clear	10
VDV826-602	RJ45	CAT 5 / CAT 5e	clear	50
VDV826-611	RJ45	CAT 5 / CAT 5e	clear	100
VDV826-603	RJ45	CAT 6	clear	25

#### **RJ45 Strain Relief Boot**

- Protects connector tabs from breaking, extending connector life.
- Minimizes cable bending that can reduce data speed and result in connector failure.
- For use with RJ45 modular data plugs.



VDV824-632

Cat. No.	Connector Type	Connector Color	Pack Qty.
VDV824-632	RJ45	black	10

#### **RJ11 Telephone Plugs**

- 6 position 4 contact for 1 or 2 line telephones.
- 6 position 6 contact for 1, 2 or 3 line telephones.





6P6C



VDV826-600

Cat. No.	Connector Type	Position & Contacts	Connector Color	Pack Qty.
VDV826-601	RJ11	6P4C	clear	25
VDV826-600	RJ11	6P6C	clear	25

#### **Insulation Displacement Connectors**

- Insulation displacement connector to add or terminate a telephone line.
- Gel-filled for moisture resistance.



VDV826-604 (26-22 AWG)



VDV826-605 (26-19 AWG)

Cat. No.	Connector Type	Position & Contacts	Connector Color	Pack Qty.
VDV826-604	UY	2P2C	yellow	25
VDV826-605	UR	3P3C	red	25





# **Voice/Data/Video Tool Kits**

#### Coax Installer Starter Kit - F-Connectors

- Includes the tools needed to prepare and connect F-Connectors.
- Durable nylon tool pouch designed specifically for F-connector installation tools.
- Additional pocket holds a screwdriver or common AA battery flashlights.
- Pouch includes a closeable pocket that will hold up to 25 compression F-connectors.
- Tunnel-loop accommodates up to 2" belt.



Cat. No.	Set Contains		Weight
VDV012-811			1.44 lbs. (0.65 kg)
	Cat. No.	Description	
	63020	multi-cable cutter	
	VDV110-802	radial cartridge stripper - coaxial cable, 2-level	
	VDV212-008	compression crimper - compact, f-connector	
	kit exclusive	5-pocket nylon tool pouch plus closeable consumables pocket	



#### LAN Installer Starter Kit - Modular

- Includes the tools needed to prepare, connect and test modular cables.
- Durable nylon tool pouch designed specifically for modular plug installation tools.
- Two additional pockets hold a screwdriver and common AA battery flashlights.
- Pouch includes a closeable pocket that will hold up to 25 RJ45 plugs.
- Tunnel-loop accommodates up to 2" belt.




	•		
Cat. No.	Set Contains		Weight
VDV026-812			1.5 lbs. (0.68 kg)
	Cat. No.	Description	
	2100-8	stainless steel electrician's scissors - free-fall	
	VDV226-011	ratcheting modular cutter/crimper/stripper	
	VDV526-052	LAN Scout™ Jr. tester	
	98554	fine point permanent marker	
	kit exclusive	5-pocket nylon tool pouch plus closeable consumables pocket	



VDV026-812

#### LAN Installer Starter Kit - Punchdown

- Includes the tools needed to prepare and connect 66 type and 110 type punchdown terminal blocks.
- Durable nylon tool pouch designed specifically for punchdown installation tools.
- Two additional pockets hold a screwdriver and common AA battery flashlights.
- Tunnel-loop accommodates up to 2" belt.



<b>Set Contains</b>		Weight
		.88 lbs. (0.40 kg)
Cat. No.	Description	
2100-8	stainless steel electrician's scissors - free-fall	•
VDV427-047	punchdown multi-tool chassis	-
VDV427-015	punchdown tool blade - 110 type	
VDV427-017	punchdown tool blade - combination 66/110 cut type	
98554	fine point permanent marker	
kit exclusive	4-pocket nylon tool pouch	-
	<b>Cat. No.</b> 2100-8 VDV427-047 VDV427-015 VDV427-017 98554	Cat. No. Description 2100-8 stainless steel electrician's scissors - free-fall VDV427-047 punchdown multi-tool chassis VDV427-015 punchdown tool blade - 110 type VDV427-017 punchdown tool blade - combination 66/110 cut type 98554 fine point permanent marker



All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.



#### **Voice/Data/Video Tool Kits**

#### **Coax Installation & Test Kit**

- Includes tools needed to prepare, connect and test coax cables.
- Coax Cable Stripper 2-Level, Radial: Designed for easy single operation cable preparations.
- Compression Crimper Compact F-Connector: Crimps compression F-connectors to coaxial cable quickly and reliably.
- Coax Explorer<sup>™</sup> Tester: Compact tool tests and verifies coaxial cable connections (good/open/short).
- Universal F-Compression Connectors RG6 / RG6-QS: Patented universal sleeve connectors install up to 5X faster.

Cat. No.	Set Contains		Weight
VDV002-818			1.1 lbs. (0.50 kg)
	Cat. No.	Description	
	VDV212-008	compression crimper - compact, F-connector	
	VDV110-061	coax cable stripper 2-level, radial	
	VDV512-057	Coax Explorer™ tester	
	VDV812-606	universal F-compression connectors - RG6/RG6-QS (10 pack)	





VDV002-818

#### **Coax Push-On Connector Installation & Test Kit**

- Includes tools needed to prepare, connect and test push-on coax cables.
- Coax Cable Stripper 2-Level, Radial: Designed for easy single operation cable preparations.
- Coax Explorer™ Tester: Compact tool tests and verifies coaxial cable connections (good/open/short).
- Push-On F-Connectors RG6 / RG6-QS: Tool-less, patented cable grip design for easy installation and strong hold.

Cat. No.	Set Contains		Weight
VDV002-820			0.28 lbs. (0.13 kg)
	Cat. No.	Description	
	VDV110-061	coax cable stripper 2-level, radial	
	VDV512-057	Coax Explorer™ tester	
	VDV812-627	push-on F-Connectors - RG6/RG6-QS (10 pack)	



#### **Modular Installation Kit**

- Includes tools needed to prepare and connect modular cables.
- Ratcheting Modular Crimper/Stripper: All-in-one tool cuts, strips and crimps paired-conductor cables (RJ11 / RJ12, RJ22, RJ45).
- Modular Data Plug RJ45 CAT5e: Thick 50 micro-inch gold plating and 3-pronged contacts with durable housing - 8 position, 8 contact for data cables.
- Telephone Plug RJ11 6P6C: Thick 50 micro-inch gold plating and 3-pronged contacts with durable housing - for 1, 2 or 3 line telephones.

Cat. No.	Set Contains		Weight
VDV226-817			0.76 lbs. (0.34 kg)
	Cat. No.	Description	
	VDV226-011	ratcheting modular crimper/stripper	
	VDV826-628	modular data plug - RJ45 - CAT5e (10 pack)	
	kit exclusive	telephone plug - RJ11 - 6P6C (10 pack)	•





VDV226-817

All dimensions are in inches and (millimeters).

AWARNING: Read carefully and understand instructions before using this tool.

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits







#### **VDV Commander**™

- Test coaxial, data (RJ45) and telephone (RJ11) cables wire map, for faults, verify shielding, continuity.
- Measure cable length and distance to a fault with Time Domain Reflectometry (TDR) technology.
- Test Power over Ethernet (PoE) systems. Detect class per IEEE 802.3af/at, test loads and identify modes.
- Locate, trace and identify cables with intergrated tone generator, Link Light, Location ID remotes and Test-n-Map™ ID Remotes.
- Perform active network (Ethernet) testing. Detect and report current link speed and link capabilities for active Ethernet drops up to 1 Gbps.
- Save up to 256 tests reports and export/print as needed.









VDV501	-829

Features		Includes
	RJ-45 8-Wire Cables	•
	F-connector Coaxial Cables	•
	Telephone Cables	With adapter
1234	Wiremap	•
×X-	Open Fault	•
$\infty$	Short Fault	•
1 1 2	Miswire Fault	•
<del>***</del>	Split-Pair Fault	•
Pass	TIA-568A/B & Crossover/Uplink	•
(?)	Active Ethernet Detects link speed and capabilities to 1 Gbps	•
1	Single-End Cable Testing	•
<b></b>	Test-n-Map™ ID Remote (Two End Testing) Test and Indentify location in one step with remote	•
PoE	Power Over Ethernet Testing	•
<del>                                      </del>	Measures Cable Length	1500 ft. / 457 m
TDR	Time Domain Reflectometry Length Measurement Method	•
±(5% + 1Ft.) ±(5% + 0.3m)	Accuracy/ Measurement Resolution	•

Features	S	Includes
	Link Light	•
ID	Cable Identification	up to 20
<b></b> 3	Shield Detection	•
<u>^</u>	Voltage Warning	•
	Low Battery Indicator	•
	Store Test Results	256
	Print Custom Reports	•
7.7	Multiple-style Tone Generator* Down to Single Conductor/Pair/Cable	4
	Color LCD Display	2.7"
	Multiple Languages	ENG · ESP · FRA
Ft./m	Imperial or Metric Results	•
Apo	Auto Power Off	•
0	Customizable Setup	•
•	USB interface (for PC connection)	MICRO
107(8)403	Upgradeable Firmware (via internet download & pc connection)	•

Cat. No.	Batteries	Battery Life	Height	Width	Depth	Weight (with batteries)	Included Accessories
VDV501-828	6 AA alkaline batteries included	20 hours active 10 years standby	6.8" (173 mm)	3.6" (91 mm)	1.85" (47 mm)	12 oz. (340 grams)	5 location RJ45 remotes,5 location F-Connector remotes, 1 test cable – micro USB to USB A, 1 test cable – universal RJ12 jumper (9"), 1 test cable – RJ45 jumper (9") 1 coax adapter – Barrel F-F Female, batteries, carrying case
VDV501-829	6 AA alkaline batteries included	20 hours active 10 years standby	6.8" (173 mm)	3.6" (91 mm)	1.85" (47 mm)	12 oz. (340 grams)	1 PROBEplus Tone Tracing Probe, 20 location RJ45 remotes, 20 location F-Connector remotes, 1 test cable – micro USB to USB A,1 test cable – universal RJ12 jumper (9"), 1 test cable – RJ45 jumper (9"), 1 coax adapter – Barrel F-F
	Probe 1 9V alkaline battery	Probe 25 hrs. active 4 yrs. standby					Female, batteries, carrying case

<sup>\*</sup>Functionality requires an analog tone tracing probe - VDV500-060 (Included with Cat. No. VDV501-829).

AWARNING: Connecting the instrument to voltages above the Safety Extra Low Voltage range of less than 60V peak AC or DC may pose a safety

**AWARNING:** The Commander<sup>™</sup> internal components are protected up to 400V peak AC or DC. Connecting the instrument to voltages above this range may pose a safety hazard to the user and the instrument.

All dimensions are in inches and (millimeters).

**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.

**AWARNING:** Always wear approved eye protection.

#### **VDV Ranger™ TDR Kit**

- Test and measure cable with the latest technology.
- Time Domain Reflectometry Spread Spectrum (TDR-SS) Technology provides accuracy up to +/-(1% + 3Ft.) by eliminating interference when measuring cable.
- TDR-SS technology broadens TDR environments by operating in Safety Extra Low Voltage (SELV) rated environments as defined by IEC. (SELV is 60 volts DC or Peak AC – 45 volts RMS).
- Measure paired-conductor cable length up to 3,000 ft. (914 m) including voice, data, video, doorbell, siamese, lamp-wire and NM cables.
- Ensure compliance and identify cable runs outside specification.
- Measure cable remaining in box or on a reel.
- Simplify cable estimating and bill jobs more accurately.
- The Tone Generator traces and identifies cables. Four tone cadences available. (Requires analog tone probe: VDV526-054 or VDV500-060 – both sold separately.)
- Includes custom designed polyester carrying case.
- Adapter cord set includes BNC to F-Connector adapter, F-Connector adapter, insulated push-on F-Connector to alligator clips, insulated BNC Connector to alligator clips and insulated push-on F-Connector to RJ45 modular plug.



Features		VDV501-815
<b>├</b>	Measures Cable Length	•
(TDR-SS)	Length Measurement Method	•
±(1% + 3Ft.) ±(1% + 1m)	Accuracy & Length Measurement	•
Maximum Cab	ole Length	3,000 ft / 914M
Maximum Cab †Must be paired co	ole Length Ranges <sup>†</sup> anductors	•
**	RJ45 8-Cables	<b>0 - 1,500 Ft</b> (457 m)
	RJ11/12 6-wire Cables	<b>0 - 2,000 Ft</b> (609 m)
-==	Coaxial Cable	<b>0 - 2,000 Ft</b> (609 m)
	Electrical Cable	<b>0 - 1,000 Ft</b> (305 m)
Ft./m	Imperial & Metric Results	•
MEM	On-Board Calibration-Memory	2 Storage Locations
××X-	Open Fault	•
$\infty$	Short Fault	•
	LCD Display	2.25 Backlit
11	Multiple Style Tone Generator	•
Apo	Auto Power Off	•
	Low Battery	•
A	Voltage Warning	•
	Interface	Multi-Adapter Set
	Carrying Case	•



VD\	/50	1-8	15

Cat. No.	Batteries	Battery Life	Height	Width	Depth	Weight (with batteries)
VDV501-815	four AA alkaline	15 hours active	6.8"	3.15"	1.30"	12 oz.
	batteries included	4 years standby	(173 mm)	(80 mm)	(33 mm)	(340 grams)

**AWARNING:** The Ranger TDR internal components are protected up to 400V peak AC or DC.

Connecting the instrument to voltages above this range may pose a safety hazard to the user and the instrument.

**AWARNING:** Connecting the instrument to voltages above the Safety Extra Low Voltage range of less than 60V peak AC or DC may pose a safety hazard to the user.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

# as 1 constants



# Voice/Data/Video Test & Measurement

#### **VDV Scout® Pro Tester Kits**

- Test continuity on data (RJ45), voice (RJ11/RJ12) and video (F-Connector coax) connections.
- Cat. No. VDV501-814 measures cable length.
- Simultaneous testing of video and data cables saves time and improves efficiency.
- Includes RJ45 & F-Connector location ID remotes for identifying cable runs to wall outlets.
- Integrated tone generator supports multiple tones and control of pins carrying tone.
- Heavy-duty ports are designed for long life and repeated connections.
- · Recessed F-Connector port for improved reliability.
- Contoured dual material chassis fits comfortably in your hand.

Feature	s	VDV501-809 Scout Pro	<b>VDV501-814</b> Scout Pro LT
***	RJ45 8-wire Cables	•	•
	RJ11/12 6-wire Cables	•	•
	F-connector Coax Cables	•	•
$\infty$	Continuity Testing	•	•
$\longleftrightarrow$	Measures Cable Length	_	•
Pass	TIA-568A/B & Crossover/Uplink	•	•
LEd	LCD Display	•	•
1 2 3 4 1 2 3 4	Wiremap		•
>>< <u>X-</u>	Open Fault	•	•
$\infty$	Short Fault	•	•
1 2 2	Miswire Fault	•	•
*****	Split Pair Fault	•	•
ID	Cable Identification – Locations Included	5	19
~~	Multiple Style Tone Generator, 4 cadence	•	•
Apo	Auto Power Off	•	•
	Low Battery	•	•
A	Voltage Warning	•	•
- <b>-</b>	Shield Detection	•	•
	Self-Storing Remote	•	•
-	Carrying Case	_	•







RJ45, F-Connector and RJ11/12 Port





CE



VDV501-809



VDV501-814

Cat. No.	Batteries	Height	Width	Depth	Included Accessories	Weight
VDV501-814	9V alkaline included	11.5" (292 mm)	8.75" (222 mm)		19 location RJ45 remotes and remote holder, 19 location F-Connector remotes and remote holder, 1 F to F Barrel Connector, battery and 1 carrying case	30 (850 g)
VDV501-809	9V alkaline included	6.3" (160 mm)	2.8" (71.2 mm)	1.70" (43.2 mm)	5 location RJ45 remotes, 5 location F-Connector remotes, 1 F to F Barrel Connector, battery and 1 remote holder	10 (283 g)

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.

#### LanMap™ Kit for VDV Scout® Pro Series Tester

- Identify and map twisted-pair infrastructure (RJ45), up to 19 locations.
- For use with VDV Scout<sup>®</sup> Pro Tester (Cat. No. VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-816).
- Heavy-duty design for long life and repeated connections.
- Remotes numbered 1 through 19 for fast and accurate identification.

Cat. No.	Height	Width	Depth	Weight	
VDV526-055	3.0" (76 mm)	3.3" (84 mm)	1.4" (36 mm)	1.9 (56 g)	



VDV526-055

#### CoaxMap™ Kit for VDV Scout® Pro Series Tester

- Identify and map coaxial cable infrastructure (F-Connector), up to 19 locations.
- For use with VDV Scout<sup>®</sup> Pro Tester (Cat. No. VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-816).
- · Heavy-duty design for long life and repeated connections.
- Remotes numbered 1 through 19 for fast and accurate identification.

Cat. No.	Height	Width	Depth	Weight
VDV512-056	3.0" (76 mm)	3.3" (84 mm)	1.0" (26 mm)	5.2 (148 g)



VDV512-056

#### Nylon Carrying Case for VDV Scout® Pro

- Designed for use with:
  - VDV Scout® Pro Tester (VDV501-053, VDV501-809)
  - VDV Scout® Pro LT Tester (VDV501-068, VDV501-814, VDV501-816)
  - Coax Map™ Kit (VDV512-056)
  - LAN Map™ Kit (VDV526-055)
- Custom designed compartments hold and protect tester and accessories securely.
- Extra cavities for additional accessories.
- Tools and accessories not included.



Shown with (Cat. No. VDV501-809)

Cat. No.	Height	Width	Depth	Weight
VDV770-080	11.5" (292 mm)	8.75" (222 mm)	2.25" (57 mm)	15 (425 g)



VDV770-080

#### Coax Explorer® Testers

- Tests and verifies coaxial cable continuity.
- Compact size fits easily into pocket or pouch.
- Bright LED indicates cable status (good/open/short).
- Simple push-button operation.
- Cat. No. VDV512-057 includes color coded remotes and a convenient remote holder to test up to 4 locations.
- Batteries included.



CE



VDV512-058

Cat. No.	Location ID	Batteries	Height	Width	Depth	Weight
VDV512-057	1	lithium non- replaceable	2.7" (69 mm)	1.1" (28 mm)	0.7" (18 mm)	1.3 (37 g)
VDV512-058	4	lithium non- replaceable	5.6" (142 mm)	1.1" (28 mm)	0.6" (16 mm)	3.3 (94 g)



VDV512-057

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.



#### LAN Scout® Jr. Tester

- Tests continuity on twisted pair data wiring (RJ45) connections.
- Integrated tone generator supports multiple tones and control of pins carrying tone.
- Heavy-duty ports are designed for long life and repeated connections.
- Compact, contoured dual-material chassis fits comfortably in your hand.

Featu	res	VDV526-052
-	RJ45 8-wire Cables	•
XX	Continuity Testing	•
Pass	TIA-568A/B & Crossover/Uplink	•
LEd	LCD Display	•
1234 1234	Wiremap	•
>> <del>\X</del> -	Open Fault	•
$\infty$	Short Fault	•
1 1 2	Miswire Fault	•
×××	Split Pair Fault	•
11	Multiple Style Tone Generator, 4 cadence	•
Apo	Auto Power Off	•
	Low Battery	•
A	Voltage Warning	•
<u>s</u>	Shield Detection	•
<b>3</b> 0	Self-Storing Remote	•



RJ45 Port



Self Storing Remote




VDV526-052

VDV501-089

Cat. No.w	Batteries	Height	Width	Depth	Weight
VDV526-052	6V – 4 x LR44	4.6"	2.3"	1.1"	4.0
	alkaline included	(117 mm)	(58 mm)	(28 mm)	(115 g)

#### **VDV Distance Meter™**





- Cable Length Measurement.
- Determines cable length up to 1,500 ft. on most paired conductor cables with accuracy +/-(5% + 1Ft.).
- Cable Manager measures cable remaining in box or on reel.
- Simplifies cable estimating and helps you bill jobs more accurately.

Cat. No.	Battery	Battery Life	Height	Width	Depth	Weight (with battery)
VDV501-089		425 hours active 4 years standby	4.9" (123 mm)	2.7" (69 mm)	1.4" (35 mm)	7.5 oz. (213 grams)

All dimensions are in inches and (millimeters).

**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.

52

**AWARNING:** Always wear approved eye protection.

#### **PROBEplus - Tone Tracing Probe**

- Trace wire paths and identify cables in common wiring systems.
- Amplifier overload LED improves accuracy, warning against misreads.
- Dual mode power button with Power-On LED indicator – tap or hold.
- Recessed buttons prevent accidental operation.
- Designed for use with Klein Tools VDV test tools (Cat. No. VDV500-051, VDV526-054, VDV526-052, VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-815, VDV501-816, VDV501-828 and VDV501-829)
- Works with many other manufacturers' analog tone generators.
- Replacement tips available (Cat. No. VDV999-065).

Cat. No.	Battery	Battery Life	Height	Width	Depth	Weight
VDV500-060	9V	25 hours active 4 years standby	9.9" (252 mm)	2.0" (51 mm)	1.14" (29 mm)	4.4 oz. (112 g) without battery 6.0 oz. (170 g) with battery




VDV500-060

Featur	Features		
O.L.	Amplifier Overload Indication	•	
101-101	Adjustable Digital Volume Control	•	
<b>3</b>	Tap-Mode Operation	•	
F	Hold-Mode Operation	•	
	Power-On LED Indicator	•	
<b>(1)</b>	Visual Notification	•	
Apo	Auto Power-Off	•	
	Low Battery Indicator	•	
<b>G</b> 5	Replaceable Tip	•	
9	Lanyard Attachme nt Loop	•	

#### **TONEcube - Tone Generator**

- Trace wire paths and identify cables in common wiring systems.
- Five discrete tracing tones.
- Constant output level over useful battery life.

CE



Cat. No.	Battery	Battery Life	Height	Width	Depth	Weight
VDV500-051	9V	120 hours active	2.7"	2.5"	1.42"	3.4 oz. (96 g) without battery
		4 years standby	(70 mm)	(63 mm)	(36 mm)	5.0 oz. (142 g) with battery



- Heavy-duty leads with rugged dual-mode modular plug for direct connection to RJ11 RJ12 and RJ45 jacks.
- Momentary slide switches prevent accidental operation.
- Designed for use with Klein Tools VDV test tools (Cat. No. VDV526-054, VDV501-060).
- Works with many other manufacturers' analog tone probes.



**AWARNING:** Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.



#### **TONEcube & PROBEplus Kit**

• Trace wire paths and identify cables in common wiring systems.

#### Kit includes:

Cat. No.

VDV500-808

- TONEcube Tone Generator and PROBEplus Tone Tracing Probe.
- Custom designed padded zipper bag.

**Set Contains:** 



		1
Cat. No.	Description	
VDV500-051	TONEcube tone generator	
VDV500-060	PROBEplus tone tracing probe	
kit exclusive	nylon pouch	



Weight





#### TraceAll™ Tone & Probe

- Trace wire paths and identify cables in common wiring systems.
- Heavy-duty RJ11 jack on tone generator for long life and repeated connections.
- Includes RJ11 adapter to convert tone generator to an alligator-clip configuration.
- Dual material chassis fits comfortably in your hand.
- Replacement tips available (Cat. No. VDV999-059).

Features	S	VDV526-054
1011	Adjustable Volume	•
11	Tone Generator, 2 Cadence	•
	Self-Storing Remote	•
<b>G</b> 5	Replaceable Tip	•
Apo	Auto Power-Off	•



VDV526-054





CE

Cat. No. Batteries Height Width Depth Weight **Included Accessories** VDV526-054 6V – 4 x LR44 RJ11 to alligator clip alkaline included (226 mm) (140 g) adapter, batteries (43 mm) (31 mm)

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.


AWARNING: Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

**AWARNING:** Do NOT use on energized circuits or cabling systems.



# **Wire Strippers/Cutters**

#### Features:



stripping holes.

#### **Wire Strippers/Cutters** KLEIN-KURVE

#### Additional Features:

- Easy-to-read markings.
- Precision shear-type blades.
- Cleanly shears 6-32 and 8-32 screws.



Cat. No.	Handle Color	Overall Length	Strips and Cuts	Screw Shearing	Weight (lbs.)
11053	blue/red	7-1/8" (181 mm)	6 – 12 AWG stranded (10 mm² – 2.5 mm²)	6-32 & 8-32	.34
11054	blue/white	7-1/8" (181 mm)	8 – 16 AWG solid (8.4 mm <sup>2</sup> – 1.3 mm <sup>2</sup> ) & 10 – 18 AWG stranded (5.3 mm <sup>2</sup> – .82 mm <sup>2</sup> )	6-32 & 8-32	.34
11055	blue/yellow	7-1/8" (181 mm)	10-18 AWG solid (4.0 mm <sup>2</sup> $-$ .75 mm <sup>2</sup> ) & $12-20$ AWG stranded (2.5 mm <sup>2</sup> $-$ .50 mm <sup>2</sup> )	6-32 & 8-32	.34
11057	blue/red	7-1/8" (181 mm)	20 - 30 AWG solid (.50 mm <sup>2</sup> $-$ .14 mm <sup>2</sup> ) & $22 - 32$ AWG stranded (.34 mm <sup>2</sup> $-$ .05 mm <sup>2</sup> )	6-32 & 8-32	.32

# **Dual NM Cable Strippers/Cutters**

#### Additional Features:

- 12/2, and 14/2 stripping slots quickly remove outer jacket of Type NM-B nonmetallic-sheathed cable.
- Stripping holes easily remove insulation on 12 and 14 AWG sold wire.
- Precision shear-type blades for square, clean cuts on solid copper wire.
- Narrow nose fits into tight places.



Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM-B Cable	Screw Shearing	Weight (lbs.)
K1412	yellow/white	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm <sup>2</sup> & 1.5 mm <sup>2</sup> )	12/2 & 14/2	6-32 & 8-32	.41


KLEIN-KURVE.

# **Dual NMD-90 Cable Strippers/Cutters**

#### Additional Features:

- Quickly removes outer jacket of Canadian NMD-90 Romex® Cable.
- Strips, cuts, and loops 12 & 14 AWG solid wires.
- Strips, cuts, and loops 14 & 16 AWG stranded wires.
- Cleanly shears 6-32 and 8-32 screws.









KLEIN TOOLS ITE





K1412CAN

0	Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NMD-90 Cable	Screw Shearing	Weight (lbs.)
ŀ	(1412CAN	yellow/white	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm² & 1.5 mm²) 14 & 16 AWG stranded (1.5 mm² & 1.0 mm²)	12/2 & 14/2	6-32 & 8-32	.41


All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.





#### **Wire Strippers/Cutters**

#### Additional Features:

- Compact, lightweight wire-stripping and cutting tools.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.
- Do not use for cutting steel wire or bolts.

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11045	yellow	6-1/4" (159 mm)	10 – 18 AWG solid (4.0 mm <sup>2</sup> – .75 mm <sup>2</sup> )	.27
11046	red	6-1/4" (159 mm)	16 – 26 AWG stranded (1.0 mm² – .14 mm²)	.27
11047	yellow	6-1/4" (159 mm)	22 - 30 AWG solid (.34 mm <sup>2</sup> 05 mm <sup>2</sup> )	.27
11049	red	6-1/4" (159 mm)	8-16 AWG stranded (6 mm <sup>2</sup> -1.0 mm <sup>2</sup> )	.27

# **Dual-Wire Stripper/Cutter**

#### Additional Features:

- Strips two wires in a single motion.
- Paired stripping holes for 14 and 12 AWG solid wire.
- One stripping hole for 10 AWG solid wire.
- Shear-type cutting blades for square, clean cuts.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11048	yellow	6-1/4" (159 mm)	10, 12, 14 AWG solid (4.0 mm², 2.5 mm², 1.5 mm²)	.27



KLEIN TOOLS

SALETN TOOLS

11045



AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.

# EST. 1857

# **Wire Strippers/Cutters**

#### **Wire Stripper/Cutter**

- Strips six standard wire sizes without nicking wire.
- Scissors action of 1/2" (13 mm) wide cutter makes clean cuts with little effort.
- Serrated nose jaws to bend, shape or pull wire; holes for looping wire ends.
- Spring-loaded for self-opening action.
- Comfortable, plastic-covered handles.

Cat. No.	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
1011	6-1/8" (156 mm)	10 - 20 AWG solid & stranded (4.0 mm <sup>2</sup> 50 mm <sup>2</sup> )	blue	.23
1011M	6-1/8" (156 mm)	0.15 - 4.0 mm <sup>2</sup> stranded wire	blue	.23



1011

#### Adjustable Wire Strippers/Cutters — Solid and Stranded Wire

- A handy, light, compact tool for stripping insulation.
- Convenient hole for looping or bending wire.
- Black-oxide finish with plastic-dipped handles.
- Cuts, strips, and loops 12-26 solid and stranded wire.
- · Adjustable slide stop with set screw for repeat stripping work.

Cat. No.	Hold-Open Spring	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
1004	yes	5" (127 mm)	12 – 26 AWG solid & stranded (2.5 mm² – 0.14 mm²)	yellow	.18
1003	no	5" (127 mm)	12 – 26 AWG solid & stranded (2.5 mm² – 0.14 mm²)	yellow	.14





1004

#### Adjustable Wire Stripper — Solid and Stranded Wire

- Simply dial desired wire size for fast, easy stripping.
- Adjustable tool makes short work of cutting and stripping operations.
- Finely honed nose cutter easily gets into tight areas.
- Wire gauge dial sets stripping dies to proper size, helps prevent nicked wire.
- Black-oxide finish with plastic-dipped handles.
- Spring-loaded design tool opens automatically after each action.

Cat. No.	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
74007	5-1/8" (130 mm)	12 – 24 AWG solid & stranded (2.5 mm² – .25 mm²)	yellow	.15



#### Katapult® Wire Stripper/Cutter

- Quick and easy 8-22 AWG wire stripping and cutting.
- Compound action wire stripping: grip and strip via single action squeezing motion.
- Precision machined stripping holes easily remove jacket insulation without damaging the wire.
- Remove up to 1" (24 mm) in length of the insulation layer (jacket layer) in a single step.
- Tension loaded wire-grip gently holds the cable in place while retaining the cable geometry.
- Recoil spring design returns tool to ready position upon cycle completion.
- Cast alloy chassis with heavy-duty Ecoat finish for corrosion resistance and durability.
- Additional precision machined steel cutting blades available.

Cat. No.	Color	Strips	Overall Length	Weight
11063W	blue/black	8-22 AWG (6 mm <sup>2</sup> – .34 mm <sup>2</sup> )	6.6" (168 mm)	12.1 oz. (0.34 g)





11063W

Cat. No.		Weight			
Replacement Blades Sets					
VDV110-046	RG6 coaxial cable replacement blades	.01			
11082	10 AWG max wire cutting blades	.01			
11073	16 – 26 AWG (1.0 mm <sup>2</sup> – .14 mm <sup>2</sup> )	.01			
Wire Stop/Gaug	ge				
11081	adjustable wire stop	.01			

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.

58

# **Wire Strippers/Cutters**

#### **Self-Adjusting Wire Stripper/Cutter**

- Strips 10-20 AWG solid, 12-22 AWG stranded, and 12/2 & 14/2 Romex<sup>®</sup> wire.
- Adjustable stopper to control the length of the core strip.
- Convenient wire cutter in handle.
- Grooved grips are designed for added comfort.



Cat. No.	Strips / Cuts	Length	Width	Depth	Weight (lbs.)
11061	10-20 AWG solid 12-22 AWG stranded 12/2 & 14/2 Romex <sup>®</sup>	8.25" (210 mm)	3.75" (95 mm)	1.25" (32 mm)	0.79

Romex® is a registered trademark of Southwire Company.

# **Combination Wire-Stripping and Cutting Tools**

#### Multi-Purpose 6-in-1 Tool

- Cleanly shears bolts.
- Easily cuts and strips wire.
- Measures stud sizes.
- Gauges wire sizes.
- Crimps insulated terminals.
- Plastic-covered cushioned handles for comfort.



1000

11061

Cat. No.	Overall Length	Strips and Cuts	Bolt Sizes	Handle Color	Weight (lbs.)
1000	7-3/4" (197 mm)	8 – 22 AWG solid (6.0 mm² – .34 mm²), 10-16 AWG stranded (4.0 mm² – 1.0 mm²)	4-40, 6-32, 8-32, 10-24, 10-32	red	.44

#### Multi-Purpose Electrician's Tool — 8-22 AWG

- Two wire cutters—one at tip, the other halfway back near stripping holes—double the utility of this tool.
- Color-coded crimping dies for 10-22 AWG insulated and non-insulated terminals.
- Cleanly shears bolts.
- Pivot nut adjusts tension.
- Wire-looping holes near tip.
- Full-sized, plastic-covered cushioned handles for comfort.





1001

1010



#### **Long-Nose Multi-Purpose Tool**

- Easily cuts and strips wire.
- Narrow, serrated pliers nose to pull, loop, and bend wire.
- Long, curved cutting blade.
- Cutters and strippers are in front of the pivot for maximum ease-of-use in reaching into tight places.
- Crimps insulated and non-insulated terminals and 7 to 8 mm ignition terminals.
- · Cleanly shears bolts.
- Plastic-covered cushioned handles for comfort.



All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.



# **Combination Tools**

# Trip-Saver® – Stainless Steel

- Unique multi-tool addresses the special needs of electricians and maintenance professionals while providing many other features handy on any job.
- Specially designed locking "L" handle snaps securely into the "L" channel, locking the fully opened blade or implement in place during use.
- Peatures the following:
  Needle-Nose Pliers, Beveled Wire Cutter,
  Toothed Pipe Grippers, Files (coarse and fine),
  5-Slot Wire Stripper (10-18) AWG, Wire-Looping Hole,
  Scraper, Awl/Reamer, Serrated Sheepsfoot Knife,
  Clip-Point Knife, Standard/Metric Ruler, Drywall Saw,
  Locking "L" Handle, #1 and #2 Phillips Hex Bits,
  Small-Slotted Hex Bit, Large-Slotted Hex Bit,
  1/4" Socket Adapter, Lanyard Hole, Nylon Pouch.



Cat. No.	Overall Length	Weight (lbs.)
1016	5-3/4" (143 mm)	.95

**AWARNING:** Close handles to lock blade in place before use.

#### **NM Cable Ripper**

- Easy-to-use cable ripper.
- Slit the outer jacket of Romex<sup>®</sup> cable (all sizes) and other nonmetallic (type NM) sheathed cable.
- Measure conductor wire gauge.

Cat. No.	Overall Length	Slits	Measures Wire Gauge	Weight (lbs.)	
74017	4" (102 mm)	all sizes of Romex <sup>®</sup> and NM	8 – 14 AWG (6 mm <sup>2</sup> – 1 mm <sup>2</sup> )	.08	
Romex® is a registered trademark of Southwire Company.					



74017

# **Crimping Tools**

# Crimping/Cutting Tools — Non-Insulated/Insulated Terminals

- Crimping die marked for insulated and non-insulated solderless terminals and connectors.
- Tapered nose design for working in confined spaces.
- Specially hardened wire cutter in nose.
- Hot-riveted joint for smooth action and no handle wobble.



1005

Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)		
1005	red	10 – 22 AWG	9-3/4" (248 mm)	.80		
Journeyman™ Series – Dual-material handles						
J1005	red/black	10 – 22 AWG	9-3/4" (248 mm)	.84		

# Crimping/Cutting Tool — Non-Insulated Terminals

- Designed for crimping non-insulated solderless terminals and connectors.
- Specially hardened wire cutter in nose.
- Tapered nose for working in confined spaces.
- Plastic-dipped cushioned handles for comfort.



Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)
1006	black	10 – 22 AWG	9-3/4" (248 mm)	.85

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.

60

# **Crimping Tools**

# Large Crimp Tool — Compound-Action



	Adjustment	screw	allows	user	to	control	crimp	depth.
--	------------	-------	--------	------	----	---------	-------	--------

Cat. No.	Crimps	Handle Color	Overall Length	Weight (lbs.)
2006	#6 – 4/0 AWG battery lugs and terminals	red	19-1/2" (495 mm)	3.80

# **Ratcheting Crimpers**

# Full-Cycle Ratcheting Crimper — Insulated Terminals

- Crimps insulated terminals in wire sizes 22-16 (front cavity), 16-14 (middle cavity), and 12-10 (rear cavity).
- Color-coded wire size markings.
- Compound lever-action of narrow-span handles puts more crimping power into each squeeze.
- Comfort-grip plastic handles.

Cat. No.	Crimps	Handle Color	Overall Length	Weight (lbs.)
T1715	10 – 22 AWG	black	9" (229 mm)	1.05

# Compound-Action Ratcheting Crimper — Insulated Terminals

- Compound-action tool crimps 10-22 AWG insulated terminals to meet or exceed MIL-SPEC pull-out tests.
- Built-in ratchet with safety release assures uniform crimps every time.
- Compound lever-action of narrow-span handles puts more crimping power into each squeeze.
- Special locator quickly positions terminal for double crimp.
- Comfort-grip plastic handles.

Cat. No.	Crimps	Handle Color	Overall Length	Weight (lbs.)
T1710	10 – 22 AWG	black	9" (229 mm)	1.05



T1715

2006



T1710

All dimensions are in inches and (millimeters).


**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.



#### Features:



#### **High-Leverage Cable Cutters**

#### Additional Features:

- High-leverage design for exceptional cutting capability.
- Precision, one-hand shearing action.
- Cable-gripping shear-type jaws.
- Perfect for working in confined spaces.
- Can be carried in most tool pouches.



63050

AWARNING: Do NOT use to cut steel or ACSR.

Cat. No.	Overall Length	Handle Color	Maximum Cable Cutting Capacity	Weight	
63050	9-1/2" (241 mm)	red	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable	.90 lbs.	
Journeyman Series – Dual-material handles					
J63050	9-9/16" (243 mm)	red and black	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable	.98 lbs.	

# Multi-Cable Cutter | KLEIN-KURVE®

- Hardened steel precision-ground cutting blades for long life.
- Copper curved cutter cleanly cuts round copper cable without compression or frayed ends.
- Anvil cutter for solid and stranded copper wire up to 12 AWG and stainless steel up to .032" (.81 mm) diameter.
- Mild steel cutter for conductors up to .080" (2 mm) diameter.
- Curved cutter for solid and stranded copper wire up to 8 AWG, multi-conductor cable up to 1/2" (13 mm) diameter and coaxial cable RG-6 Quad, RG-59, and RG-62.
- Double-dipped grips for comfort.
- · Coil spring provides fast self-opening action.
- Holes for looping and bending wire.
- Handy closure lock for convenient storage.



Cat. No.	Overall Length	Screw Shearing	Handle Color	Weight
63020	7" (177 mm)	6-32 & 8-32	red	.44 lbs.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



#### Cable Cutters — Coaxial

- Cable-gripping jaws quickly score jacket and insulation, and easily cut through copper inner conductor.
- Blades cleanly cut aluminum and copper coaxial cable without compression and frayed ends.
- Forged body with heat-treated and precision-ground steel blade withstands frequent cutting.
- Hot-riveted design requires no adjustment while maintaining a smooth, precise operation.
- Compact, lightweight design fits perfectly in any professional's tool pouch.
- Handles are plastic-coated for maximum comfort and gripping power.
- When cutting drop wire with an inner steel conductor, we recommend Cat. No. D2000-28 diagonal-cutting pliers.



AWARNING: Do NOT use to cut steel or ACSR.

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	Handle Color	Weight
63028	8-1/4" (216 mm)	.75" (19 mm) diameter	yellow	.80 lbs.
63030	8-1/4" (216 mm)	1" (25 mm) diameter	blue	.83 lbs.

#### **Compact Cable Cutter**

- Precise, one-hand shearing action cuts 24 AWG copper, aluminum multi-strand cable and wire, and 100-pair telephone cable.
- Special shear angle cuts cleanly without compression to cable geometry for telecom cable work.
- Heat-treated, high-carbon steel shearing edges for long life.
- Forged body with 3/8" (10 mm) case-hardened rivet.
- Plastic-dipped handles for comfort.
- Not designed for cutting steel or ACSR.



63055

AWARNING: Do NOT use to cut steel or ACSR.

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Handle Color	Weight
63055	8" (203 mm)	24 AWG copper, aluminum multi-strand cable and wire, and 100-pair telephone cable	red	.65 lbs.

#### **All-Purpose Shears and BX Cutter**

- High-leverage, shear-type design for one-hand operation.
- Lightweight and compact.
- Stripping notch for added convenience.
- Cuts a variety of materials including cable, sheet metal, steel strapping, and bundling wire.
- Handle cavity is designed to restore BX cable to original shape after cutting.
- Plastic-dipped handles for comfort.



Cat. No.	Overall Length	Length of Cut	Handle Color	Weight
1104	7-5/8" (194 mm)	7/8" (22 mm)	red	.60 lbs.

#### **Heavy-Duty Cable Shears**

- Heavy-duty, tempered steel blades.
- Blades grip cable and cut easily at center of jaws.
- Lock keeps handles closed for easy storage.
- Comfortable, plastic-coated handles for steady grip.
- Hardened steel, precision cutting blades for long service life.
- Unique triangular jaws cleanly cut cable without compression or frayed ends.
- Lightweight tool perfect for overhead cutting.



63016

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Handle Color	Weight
63016	7-1/2" (191 mm)	up to 1/4" copper and mild steel strands, up to 3/16" aircraft cable, wire rope, aluminum and copper rods, up to 5/32" for steel & iron rods	blue	.65 lbs.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



#### **Utility Cable Cutter**

- Forged steel with black-oxide finish for long life.
- Shear-type hook jaws grab and hold cable while shear-cutting action makes clean cuts.
- Beveled tips for positive mating.
- Hinge bolt with pin-set nut for proper blade tension.
- Non-slip vinyl grips.



63035

Cat. No.	Overall Length	MCM Cable-Cutting Maximum Capacity*	Handle Color	Weight
63035	16-3/4" (425 mm)	350 copper, 350 aluminum	red	1.70 lbs.
* Not designed for cutting steel or ACSR.				

# **Wire Rope Cutter**

- Shear type blades for square, clean cuts.
- All forged construction; USA Steel.
- Non-slip vinyl grips.
- Hinge bolt with pin-set nut for proper blade tension.
- Cuts wire up to 9/32" (7 mm) and Stoffel<sup>®</sup> container seals.



63035SC

Cat. No.	Overall Length	Cuts	Maximum Cutting Capacity	Handle Color	Weight
63035SC	18" (457 mm)	Stoffel Seals®	9/32" (7 mm) wire rope and cables	red	2.00 lbs.

Stoffel® is a registered trademark of Stoffel Seals Corporation.

#### **Standard Cable Cutters**



63041TH

- Beveled tips assure positive mating, and hinge on a rugged bolt with a pin-set nut to maintain proper blade tension.
- Makes a clean, even cut for ease in fitting lugs and terminals.
- Not designed for cutting steel or ACSR.
- Includes rubber sleeves (Cat. No. 63041TH).

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	MCM Cable-Cutting Maximum Capacity	Weight
63041	25-1/2" (648 mm)	1-3/8" (35 mm) diameter	500 copper, 750 aluminum	5.25 lbs.
63041TH	25-1/2" (648 mm)	1-3/8" (35 mm) diameter	500 copper, 750 aluminum	5.25 lbs.
63045	32" (813 mm)	1-3/4" (44 mm) diameter	1000 copper, 1200 aluminum	8.00 lbs.
Replaceme	nt Cable Cutter Heads	(complete)	Fits Klein Cat. No.	
63081			63041	2.05 lbs.
63090			63045	3.30 lbs.

All dimensions are in inches and (millimeters).

**AWARNING:** Do NOT use to cut steel or ACSR.

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock



#### **Communications Cable Cutter**



#### **Ratcheting Cable Cutters**

- High-leverage ratchet mechanism for single-handed cutting of copper and aluminum cables, leaving no burrs or sharp edges.
- Patented two-step ratchet mechanism requires fewer strokes per cut.
- Quick release lever opens blades easily in every cutting position. (Allows removal of the cable before completion of cut).
- Precision ratcheting mechanism holds cable tight and allows rapid, straight cuts with minimum effort.
- Hardened steel cutting blades for lasting strength and sharpness.
- Plastic covered handles with hand guards for comfort and firm grip.
- Locking lever keeps handles closed for easy transport; fits in a toolbox or bag.
- One-year warranty.







**AWARNING:** Do NOT use to cut steel or ACSR.

	MCM Maximum Cable Capacity						
Cat. No.	Copper	Aluminum	ACSR	Communication Cable	Overall Length	Handle Color	Weight
63060	400 MCM (185 mm <sup>2</sup> )	600 MCM (300 mm <sup>2</sup> )	_	1-1/8" (28 mm)	10-1/4" (260 mm)	red	1.32 lbs.
63711	600 MCM (300 mm <sup>2</sup> )	750 MCM (400 mm <sup>2</sup> )	_	1-1/8" (28 mm)	11-1/2" (292 mm)	red	2.00 lbs.
63750	1000 MCM (500 mm <sup>2</sup> ) Frequent Use: 750 MCM (400 mm <sup>2</sup> )	1000 MCM (500 mm <sup>2</sup> ) Frequent Use: 750 MCM (400 mm <sup>2</sup> )	_	2-1/16" (52 mm)	12-1/8" (308 mm)	red	1.76 lbs.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



66

#### **ACSR Ratcheting Cable Cutter**


- Cutting inserts are easily replaced by simply removing 3 screws per blade.
- Capacity: 477 MCM ACSR
   1-1/4" (32 mm) Ø CU-AL Stranded
   1" (25 mm) Ø CU Solid
   1/2" (13 mm) Ø Guy Strand (NOT FOR EHS)
- Tool can be locked when not in use.
- High-leverage ratcheting mechanism for easier cutting.
- Plastic covered handles with hand guards for comfort and firm grip.
- At a length of just under 14" tool can be carried in a tool pouch.
- Cleanly cuts 336 MCM Linnet ACSR and 2/0 triplex steel messenger cable (Cat. No. 63607).



63607



	MCM Maximum Cable Capacity						
Cat. No.	ACSR	Stranded Aluminum & Copper	Solid Copper	Guy Strand	Length	Handle Color	Weight
63607	336 MCM (170 mm <sup>2</sup> )	600 MCM (300 mm <sup>2</sup> )	400 MCM (185 mm <sup>2</sup> )	_	10-1/4" (260 mm)	yellow	1.50 lbs.
63800ACSR	477 MCM (273 mm <sup>2</sup> )	1-1/4" (32 mm)	1" (25 mm)	1/2" (13 mm)	13-3/4" (349 mm)	red	3.20 lbs.
Replaceme	ent Cutting Inserts (	(with set of 6 screws)	Fits Klein Cat. No.				
63858			63800ACSR				



**AWARNING:** Always wear approved eye protection.


**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.





#### Ratcheting Cutter — Heavy-Duty

- Ratchet-action design provides maximum leverage with minimum effort for heavy-duty use.
- Cuts steel and ACSR.
- Forged, heat-treated, shear-type blades, plus plus 17" (432mm) long fiberglass handles with heavy duty grips for comfort and slip resistance.



• Not designed for cutting EHS guy strand or reinforcement rod.

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	Communications Cable-Cutting Maximum Capacity	Weight
63700	28" (711 mm)	2-1/4" (57 mm) diameter	1-1/4" (32 mm) dia. ACSR, ACAR 7/16" (11 mm) dia. common guy strand 5/8" (16 mm) dia. steel wire rope 1/2" (13 mm) dia. steel rod (C.R.S. SOFT)	14.00 lbs.

750 MCM (1-3/8" dia.) (35 mm) copper or aluminum

**Bolt Cutters** 

#### **Bolt Cutters**

- All-purpose, center-cut jaws for soft, medium, and hard metals.
- Forged, alloy tool steel jaws are precision ground for sure, efficient cutting and long life.
- Lockplate reinforcement prevents jaw bolts from loosening or turning, keeps jaws in correct alignment.
- One adjustment realigns cutting edges.
- 3-point toggle joint multiplies 50 lbs. of hand pressure on handles to 4,000 pounds at cutting jaws.

No.	Туре	Length	Cutting Max. Capacities*	Cutting Max. Capacities**	Color	, and the second
Steel H	andle					
63314	steel	14" (356 mm)	5/16" (8 mm)	3/16" (5 mm)	red	3.15 lbs.
63318	steel	18" (457 mm)	3/8" (10 mm)	1/4" (6 mm)	red	3.55 lbs.
63324	steel	24" (610 mm)	7/16" (11 mm)	5/16" (8 mm)	red	6.30 lbs.
63330	steel	30" (762 mm)	1/2" (13 mm)	3/8" (10 mm)	red	10.20 lbs.
63336	steel	36" (914 mm)	9/16" (14 mm)	7/16" (11 mm)	red	14.25 lbs.
63342	steel	42" (1067 mm)	11/16" (18 mm)	1/2" (13 mm)	red	19.20 lbs.
Fibergl	ass Handle					
63118	fiberglass	18-1/4" (464 mm)	3/8" (10 mm)	1/4" (6 mm)	red	3.65 lbs.
63124	fiberglass	24-1/2" (622 mm)	7/16" (11 mm)	5/16" (8 mm)	red	6.13 lbs.
63130	fiberglass	30-1/2" (775 mm)	1/2" (13 mm)	3/8" (10 mm)	red	9.50 lbs.
63136	fiberglass	36-1/2" (927 mm)	9/16" (14 mm)	7/16" (11 mm)	red	12.95 lbs.

Cat. Handle Overall Soft & Medium Hard Material Handle Weight

* Up to Brinell 300, Rockwell C31
** Up to Brinell 400, Rockwell C4

Replacement Bolt Cutter Heads (complete) Cat. No. Fits Cat. No. Weight 63214 63314 1.00 lbs 1.25 lbs. 63218 63118, 63318 63224 63124, 63324 2.10 lbs. 63230 63130, 63330 3.40 lbs. 63242 63342 5.95 lbs.

63700

63124

Replacement Fiberglass Handle Sets				
Cat. No.	Fits Cat. No.	Weight		
63119	63118	2.15 lbs.		
63125	63124	3.76 lbs.		
63131	63130	5.56 lbs.		
63137	63136	7.55 lbs.		

AWARNING: NOT for cutting cable.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.







#### **Bolt Cutters**

#### **Bolt Cutters** — **Heavy-Duty**



- Steel handles and precision ground, forged alloy tool steel jaws.
- Lever design creates 4,000 lbs. jaw pressure with 50 lbs. hand pressure.
- Handles have heavy vinyl grips with flat grip ends for 90° cuts.

Cat. No.	Overall Length	Soft & Medium Cutting Maximum Capacities*	Hard Material Cutting Maximum Capacities**	Weight
Steel Hand	dle			
63524	24" (610 mm)	7/16" (11 mm)	5/16" (8 mm)	7.10 lbs.
63530	30" (762 mm)	1/2" (13 mm)	3/8" (10 mm)	11.65 lbs.
63536	36" (914 mm)	9/16" (14 mm)	7/16" (11 mm)	16.35 lbs.
63542	42" (1067 mm)	11/16" (18 mm)	1/2" (13 mm)	21.00 lbs.

63542	42" (1067 mm)	11/16" (18 mm)	
* Up to Br	rinell 300, Rockwell	C31.	

\*\* Up to Brinell 400, Rockwell C42.

Replacement Bolt Cutter Heads (complete)					
Cat. No.	Fits Cat. No.	Weight			
63636	63536	6.50 lbs.			
63642	63542	8 70 lbs			


63536


#### **Cable Benders**

- Forged, one-piece steel construction for exceptional durability and high strength to meet the most demanding job requirements.
- Head is angled 22° for ease in bending cable in tight, hard-to-access places.
- Corrosion-resistant, black-oxide finish with heavy-duty double-dipped plastic handle.
- Handle is contoured for a firm, comfortable grip.
- It is recommended that two benders be used for easier bends.

Cat. No.	Overall Length	Tool Opening	Maximum Cable Capacity	Weight
50400	12" (305 mm)	7/8" (22 mm)	350 MCM	.90 lbs.
50402	14-1/2" (367 mm)	1-1/64" (26 mm)	500 MCM	1.55 lbs.







**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.





69

# Introduction – Insulated Tools – Classic



All Classic Klein insulated tools comply with ASTM F-1505 and IEC 60900-2004 standards for insulated tools and are clearly marked with the official international 1000-volt rating symbol. Not all tools with plastic coatings or plastic handles provide protection against electrical shock. The large, bright orange handles make the tool comfortable to use all day and easy to identify in the field. Only use those tools that are marked with the official international 1000-volt rating symbol, as shown, if there is any chance that the tool will make contact with an energized source.

#### **Insulated Pliers – Classic**



All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

**AWARNING:** Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.





**Insulated High-Leverage Side-Cutting Pliers** 

# Additional Features:

- High-leverage design provides 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length
D213-9NE-INS	New England	9-5/8" (245 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)
2000 Series* -	Heavy-duty cutting	knives				
D2000-9NE-INS	New England	9-5/8" (245 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)
		· · · · · · · · · · · · · · · · · · ·	11 0 0 111	1 .1 6 . 1	, ,	

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

# Insulated High-Leverage Side-Cutting Pliers — Connector Crimping

#### Additional Features:

· Crimping die behind hinge for superior leverage.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	
D213-9NECR-INS	New England	9-5/8" (245 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)	

# Insulated High-Leverage Universal Side-Cutting Pliers — Connector Crimping

#### Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals.
- Toothed pipe-grip for greater power.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length
12098-INS	Universal	8-7/8" (225 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	1/2" (13 mm)	3/4" (19 mm)

# **Insulated High-Leverage Diagonal-Cutting Pliers**

## Additional Features:

 High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives
D228-8-INS	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard
2000 Series* - H	leavy-duty cutting knives				
D2000-28-INS	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

**AWARNING:** Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



72

# Insulated High-Leverage Diagonal-Cutting Pliers — Angled Head

#### Additional Features:

- Angled head for easier work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives
D248-8-INS	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard
2000 Series* - F	Heavy-duty cutting knives				
D2000-48-INS	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard

<sup>\*</sup>Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

# Insulated Heavy-Duty Diagonal-Cutting Pliers — Tapered Nose

#### Additional Features:

- Heavy-duty tapered nose design.
- One-inch deep jaws easily reach into confined spaces.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives
D220-7-INS	7-7/8" (200 mm)	1" (25 mm)	31/32" (25 mm)	1/2" (13 mm)	standard

# Insulated Heavy-Duty Long-Nose Pliers — Side-Cutting

#### Additional Features:

- Induction hardened cutting knives for long life.
- · Heavier design for easier, more comfortable cutting.
- Extended handles provide added reach and leverage.
- Cat. No. D203-8N-INS has skinning hole for No. 12 AWG wire.





Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
D203-8-INS	8-7/8" (225 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)
D203-8N-INS	8-7/8" (225 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.



# Additional Features:

- Induction hardened cutting knives for long life.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	
D203-6-INS	6-7/8" (175 mm)	1-15/16" (49 mm)	11/16" (17 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	
D203-7-INS	7-3/8" (187 mm)	2-7/16" (62 mm)	11/16" (17 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	

# **Insulated Pump Pliers**

# Additional Features:


	and groove design for even with heavy pressure.		1		4		
Cat. No.	Overall Length	Max. Jaw Capacity			7	D502-1	U INIC
)502-10-INS	10-1/4" (260 mm)	1-3/4" (44 mm)				D302-1	0-1143

# **Insulated Crimping/Cutting Tool — Classic**

# **Insulated Crimping/Cutting Tool**

#### Additional Features:

- Tapered nose designed for working in confined spaces.
- Crimping dies marked for insulated and non-insulated solderless terminals and connectors.
- Accommodates wire from No. 10 to 22 AWG.
- Wire cutter in nose.



# 1005-INS

# **Insulated Cable Cutter - Classic**

# **Insulated High-Leverage Cable Cutter**

# Additional Features:

- Special, high-leverage design for exceptional cutting capability.
- Cable-gripping shear-type jaws.
- · Precision, one-hand shearing action.
- Perfect for working in confined spaces.

Cat. No.	Overall Length	Cuts Up to
63050-INS	9-5/8" (245 mm)	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable



AWARNING: Do NOT use to cut steel or ACSR.

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.



# **Insulated Wire Stripper/Cutter**

#### Additional Features:

- Cuts, strips, loops and gauges wire.
- Spring-loaded for self-opening.
- · Compact, lightweight wire-stripping, cutting tool.
- Narrow nose fits into tight places.
- Do not use for cutting steel wire or bolts.
- Hardened spring steel with precision-ground stripping holes for easy removal of insulation.



11049-INS

Cat.No.	Overall Length	Strips and Cuts	Handle Color
11045-INS	7" (178 mm)	10, 12, 14, 16, 18 solid AWG (4.0 mm², 2.5 mm², 1.5 mm², 1.0 mm², 0.75 mm²)	orange
11049-INS	7" (178 mm)	8, 10, 12, 14, 16 stranded AWG (6.0 mm², 4.0 mm², 2.5 mm², 1.5 mm², 1.0 mm²)	orange

# Insulated Wire Stripper/Cutter KLEIN-KURVE

#### Additional Features:

- Cuts, strips, loops and gauges both solid and stranded wire.
- Spring-loaded for self-opening.
- Serrated nose for easy bending, shaping and pulling of wire.
- Cleanly shears 6-32 and 8-32 scews.
- Do not use for cutting steel wire.

Cat.No.	Overall Length	Strips and Cuts	Handle Color
11055-INS	8" (203 mm)	10, 12, 14, 16, 18 AWG solid 12, 14, 16, 18, 20 AWG stranded	orange







All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

# **Introduction – Electrician's Insulated Pliers**





**Durable**, three component molded insulation provides protection against electric shock.

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

Forged steel handle.



Klein electrician's insulated tools meet or exceed IEC 60900: 2012, ASTM F1505, and VDE standards.

They are clearly marked with the official 1000-volt rating symbol.

Multi-color, sleek design with small thumb quards for ease of handling and storage. A flame retardant, impact-resistant, multi-color outer coating.



The Electrician's line of insulated tools provides a multi-color, sleeker design than the Classic Lineman's insulated tools. 1000V rated and individually tested to conform to ASTM F1505, IEC 60900. EINS tools have passed VDE third party testing certification to the IEC 60900 standard. This line of tools provides the everyday protection the electrician needs in a compact, lightweight design.

Catalog numbers for Klein electrician's insulated tools have the suffix "EINS" and are marked with the official international 1000-volt rating symbol. Not all tools with plastic coatings or plastic handles provide protection against electrical shock. Only use those tools that are marked with the official international 1000-volt rating symbol, as shown, if there is any chance that the tool will make contact with an energized source.





# **Electrician's Insulated Pliers**

# **Electrician's Insulated High-Leverage Side-Cutting Pliers**

# Additional Features:

- High-leverage design provides 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.
- 2000 Series cuts ACSR, screws, nails and most hardened wires.



213-9NE-EINS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length
213-8NE-EINS	New England	8-13/16" (224 mm)	1-7/16" (37 mm)	1-7/64" (28 mm)	5/8" (16 mm)	3/4" (19 mm)
213-9NE-EINS	New England	9-5/8" (245 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)
2000 Series* -	Heavy-duty cutting	knives				
2000-9NE-EINS	New England	9-5/8" (245 mm)	1-19/32" (41 mm)	1-5/16" (33 mm)	5/8" (16 mm)	25/32" (20 mm)
*Cute ACSR screw	e naile and most hard	dened wire Features combination	n nolished and black-oxide	finish		

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white laver shows through orange laver.

AWARNING: Do NOT use screwdrivers to pry or chisel

AWARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.





# **Electrician's Insulated Combination Pliers**

#### Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals.
- Toothed pipe-grip for greater power.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length
12098-EINS	Universal	8-7/8" (225 mm)	1-25/32" (45 mm)	1-1/32" (26 mm)	1/2" (13 mm)	3/4" (19 mm)

# Electrician's Insulated High-Leverage Diagonal Cutting Pliers

#### Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.
- Cuts ACSR, screws, nails, and most hardened wire.
   Features combination polished and black-oxide finish.



2000-28-EINS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length
2000-28-EINS	tapered	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard

# Electrician's Insulated High-Leverage Diagonal Cutting Pliers — Angled Head

#### Additional Features:

- Angled head for easier work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.
- Cuts ACSR, screws, nails, and most hardened wire.
   Features combination polished and black-oxide finish.

(S)	
	2000-48-EINS

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives
2000-48-EINS	8-1/4" (210 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard

# **Electrician's Insulated Cable Cutter**

# **Electrician's Insulated High-Leverage Cable Cutter**

- · High-leverage design for exceptional cutting capability.
- Cable-gripping shear-type jaws.
- Precision, one-hand shearing action.
- Perfect for working in confined spaces.

AWARNING: Do NOT use to cut steel or ACSR.



Cat.No.	Overall Length	Cuts Up to
63050-EINS	9-5/8" (245 mm)	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.





# **Electrician's Insulated Pliers**





# Electrician's Insulated Long-Nose Pliers — Side-Cutting

#### Additional Features:

- Induction hardened cutting knives for long life.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.
- Extended handles provide added reach and leverage.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
203-6-EINS	6-7/8" (175 mm)	1-15/16" (49 mm)	11/16" (17 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)
203-7-EINS	7-3/8" (187 mm)	2-7/16" (62 mm)	11/16" (17 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)
203-8-EINS	8-7/8" (225 mm)	2-5/16" (59 mm)	1" (25 mm)	1/2" (13 mm)	5/8" (16 mm)	1/8" (3 mm)

# Electrician's Insulated Tongue & Groove Pliers

 Secure tongue and groove design for non-slip grip – even with heavy pressure.





# **Electrician's Insulated Stripper/Cutters**

# Electrician's Insulated Solid & Stranded Stripper

## Additional Features:

- Cuts, strips, loops and gauges both solid and stranded wire.
- Spring loaded for self-opening.
- Serrated nose for easy bending, shaping and pulling of wire.
- Cleanly shears 6-32 and 8-32 screws.
- Do not use for cutting steel wire.



Cat.No.	Overall Length	Strips and Cuts
11054-EINS	8" (203 mm)	8 – 16 AWG solid (8.4 mm² – 1.3 mm²) & 10 – 18 AWG stranded (5.3 mm² – .82 mm²)

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

**AWARNING:** Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.



78

# **Insulated Screwdrivers and Nut Drivers**

# Features:



Klein insulated tools meet or exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and are clearly marked with the official 1000-volt rating symbol.



Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications.

Custom, US-made tool steel.

Durable, two layer, molded insulation.

Patented Tip-Ident® quickly identifies nut driver size.

**Cushion-Grip handles** 

for greater torque

and comfort.



Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

Bright orange outer coating is flame and impact resistant.

# **Insulated Screwdrivers**

# Insulated Phillips-Tip - Round-Shank Screwdrivers

# Additional Features:

- Klein's profilated Phillips-tip provides a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Square-Recess tips are perfect for electrical, telephone and work in recessed holes and other tight spaces.





661-7-INS

Cat. No.	Point Size	Shank Length	Overall Length
1 Insulat	ted Phillips Tip		
633-4-INS	#1	4" (102 mm)	7-3/4" (197 mm)
603-4-INS	#2	4" (102 mm)	8-5/16" (212 mm)
603-7-INS	#2	7" (178 mm)	11-5/16" (288 mm)
633-7-INS	#3	7" (178 mm)	12-3/8" (315 mm)
Insulat	ted Cabinet Tip		
607-3-INS	3/32" (2.4 mm)	3" (76 mm)	6-3/4" (171 mm)
612-4-INS	1/8" (6 mm)	4" (102 mm)	7-3/4" (197 mm)
601-4-INS	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)
601-7-INS	3/16" (5 mm)	7" (178 mm)	10-3/4" (273 mm)
602-4-INS	1/4" (6 mm)	4" (102 mm)	8-5/16" (212 mm)
605-7-INS	1/4" (6 mm)	7" (178 mm)	11-5/16" (288 mm)
602-7-INS	5/16" (8 mm)	7" (178 mm)	12-3/8" (315 mm)
602-8-INS	3/8" (9.5 mm)	8" (204 mm)	13-3/8" (340 mm)

Cat. No.	Point Size	Shank Length	Overall Length
O Insulat	ted Square-Rec	ess Tip	
661-4-INS	#1	4" (102 mm)	8-5/16" (212 mm)
661-7-INS	#1	7" (178 mm)	11-5/16" (288 mm) <b>NEW!</b>
662-4-INS	#2	4" (102 mm)	8-5/16" (212 mm)
662-7-INS	#2	7" (178 mm)	11-5/16" (288 mm) <b>NEW!</b>

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white laver shows through orange laver.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.



2-Piece Insulated 4" Screwdriver Set

# Additional Features:

• Includes one 1/4" cabinet tip and one #2 Phillips tip.



Cat. No.	Set Contain	S			
33532-INS					
	Cat. No.	Description	Shank Tip Width	Shank Length	Overall Length
	602-4-INS	round-shank, cabinet-tip	1/4" (6 mm)	4" (102 mm)	8-5/16" (211 mm)
	603-4-INS	round-shank, profilated Phillips-tip	#2	4" (102 mm)	8-5/16" (211 mm)

# **Insulated Nut Drivers**

# 6" Insulated Hollow-Shaft Nut Drivers

## Additional Features:

- Slimmer molded insulation with increased durability.
- Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications.

Cat. No.	Color Code	Hex Size	Overall Length
646-3/16-INS	black	3/16"	9-3/4" (248 mm)
646-1/4-INS	red	1/4"	9-3/4" (248 mm)
646-5/16-INS	yellow	5/16"	9-3/4" (248 mm)
646-11/32-INS	green	11/32"	9-3/4" (248 mm)
646-3/8-INS	blue	3/8"	10-5/16" (262 mm)





646-5/8-INS

Cat. No.	Color Code	Hex Size	Overall Length
646-7/16-INS	brown	7/16"	10-5/16" (262 mm)
646-1/2-INS	red	1/2"	11-3/8" (289 mm)
646-9/16-INS	orange	9/16"	11-3/8" (289 mm)
646-5/8-INS	yellow	5/8"	11-3/8" (289 mm)

# **Insulated Skinning Knife**

# **Insulated Lineman's Skinning Knife**

#### Additional Features:

- Molded measuring marks on back of handle to help measure stripping length of wire.
- Large molded handle for an easier, more comfortable grip.
- Tough, tempered steel blade provides maximum sharpness and durability to withstand frequent cable scoring.

Cat. No.	Blade Length	Handle Color	Overall Length
1571-INS	2 3/8" (60 mm)	orange	8-3/4" (223 mm)



1571-INS

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.



# General-Purpose Insulated 22-Piece Tool Kit

- Case includes three pallets with customfitted pockets for each tool, piano-hinged cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions:
   7-3/4" W x 14-1/4" D x 8" H
   (451 mm x 362 mm x 203 mm).
- Overall dimensions:
   18-7/8" W x 15-3/8" D x 8-1/4" H
   (479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33537) available.

See individual tool listings for more details.



Cat. No.	Kit Contains	Weight
33527		24.30 lbs. (11 kg)

Cat. No.	Description
D2000-9NE-INS	insulated side-cutting pliers
12098-INS	insulated universal side-cutting pliers
D2000-28-INS	insulated diagonal-cutting pliers
D2000-48-INS	insulated diagonal-cutting pliers – angled head
D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting
D220-7-INS	insulated diagonal-cutting pliers – tapered nose
D203-6-INS	insulated long-nose pliers – side-cutting
D203-7-INS	insulated long-nose pliers – side-cutting
601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")
601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")
612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
D502-10-INS	insulated pump pliers
11045-INS	insulated wire stripper/cutter
63050-INS	insulated high-leverage cable cutter
1571-INS	insulated lineman's skinning knife
1005-INS	insulated crimping/cutting tool
33537	extra-sturdy, bright-yellow case

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.





# **Utility Insulated 13-Piece Tool Kit**

- The custom case includes two pallets with custom-fitted pockets for each tool, piano-hinged case cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Inside dimensions: 17-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm).
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm).
- Replacement case (Cat. No. 33535) available.

Cat. No.	Kit Contains		Weight
33525			20.05 lbs. (9 kg)
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	•
	D2000-28-INS	insulated diagonal-cutting pliers	
	D2000-48-INS	insulated diagonal-cutting pliers – angled head	
	D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting	_
	602-4-INS	insulated cabinet-tip –	
		round-shank screwdriver (1/4" x 4")	
	602-7-INS	insulated cabinet-tip –	
		round-shank screwdriver (5/16" x 7")	
	602-8-INS	insulated cabinet-tip –	
		round-shank screwdriver (3/8" x 8")	-
	633-4-INS	insulated Phillips-tip –	
		round-shank screwdriver (#1 x 4")	



Cat. No.	Description
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535	extra-sturdy, bright-yellow case

# **Utility Insulated 13-Piece Tool Kit**

- The light, compact, soft roll-up carry case provides protective storage with custom-fitted pockets for each tool.
- Kit includes a padded, adjustable shoulder strap.
- Case dimensions:
   Opened 24-1/2" x 24-1/2" (622 mm x 622 mm).
   Closed 24-1/2" x 5-1/2" (622 mm x 140 mm).
- Replacement roll-up case (Cat. No. 33535SC) available.

Cat. No.	Kit Contains		Ī
33525SC			(
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	
	D2000-28-INS	insulated diagonal-cutting pliers	
	D2000-48-INS	insulated diagonal-cutting pliers – angled head	
	D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
	602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
	633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	

Weight 9.75 lbs. (4.4 kg)



Cat. No.	Description
603-4-INS	insulated Phillips-tip –
	round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip –
	round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535SC	roll-up soft case with shoulder strap

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

# **Insulated 8-Piece Tool Kits**

- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets.
- Overall case dimensions are:
   15-1/2" W x 11" D x 2-1/2" H
   (394 mm x 279 mm x 64 mm).
- Replacement case (Cat. No. 33536) available.

See individual tool listings for more details.

# ht. s. (3 kg)

# **Premium Insulated 8-Piece Tool Kit**

Cat. No.	Kit Contains		Weight
33529			6.90 lbs. (3 kg
	Cat. No.	Description	
	D2000-9NE-INS	insulated side-cutting pliers	
	D2000-48-INS	insulated diagonal-cutting pliers	
	D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	<del></del>
	63050-INS	insulated high-leverage cable cutter	
	11055-INS	insulated wire stripper/cutter	
	33536	heavy-duty polyester case	

# **Basic Insulated 8-Piece Tool Kit**

Cat. No.	Kit Contains		Weight
33526			6.90 lbs. (3 k
	Cat. No.	Description	
	D213-9NE-INS	insulated side-cutting pliers	
	D228-8-INS	insulated diagonal-cutting pliers	
	D203-8N-INS	insulated heavy-duty long-nose pliers – side-cutting	
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
	63050-INS	insulated high-leverage cable cutter	
	11045-INS	insulated wire stripper/cutter	
	33536	heavy-duty polyester case	

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

AWARNING: Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

**AWARNING:** Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.





# 9-Piece Insulated Screwdriver Kit

- Nine-piece insulated screwdriver assortment with three sizes of each tip style: cabinet, keystone, and Phillips.
- Highly durable, black nylon case features: coil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall dimensions: 5-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33538) available.

See individual tool listings for more details.

Cat. No.	Kit Contain	IS .	Weight
33528			5.40 lbs. (2.4 kg)
	Cat. No.	Description	
	601-4-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 4")	
	601-7-INS	insulated cabinet-tip – round-shank screwdriver (3/16" x 7")	
	612-4-INS	insulated cabinet-tip – round-shank screwdriver (1/8" x 4")	
	602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")	
	602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")	
	602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")	
	633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")	
	603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")	
	633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")	
	33538	heavy-duty polyester case	



33528

# **Cushion-Grip Insulated 9-Piece Nut Driver Kits**

- Nine-piece insulated nut driver assortment of popular sizes.
- Individually tested to exceed standards.
- Two layers of insulation provide protection against electric shock.
- Highly durable, black nylon case features: oil-zipper closure, polypropylene handles, custom-fitted tool pockets, extra pocket is provided for storage of papers or other items.
- Overall case dimensions are: 15" W x 12-3/4" L x 3-1/2" D (381 mm x 324 mm x 89 mm).

Replacement case available Cat. No. 33534.

See individual tool listings for more details.

Cat. No.	Kit Contains		Weight
33524			6.00 lbs. (2.7 kg)
	Cat. No.	Description	
	646-3/16-INS	insulated 3/16" hollow shaft nut driver, 6" shaft	
	646-1/4-INS	insulated 1/4" hollow shaft nut driver, 6" shaft	
	646-5/16-INS	insulated 5/16" hollow shaft nut driver, 6" shaft	
	646-11/32-INS	insulated 11/32" hollow shaft nut driver, 6" shaft	_
	646-3/8-INS	insulated 3/8" hollow shaft nut driver, 6" shaft	_
	646-7/16-INS	insulated 7/16" hollow shaft nut driver, 6" shaft	
	646-1/2-INS	insulated 1/2" hollow shaft nut driver, 6" shaft	
	646-9/16-INS	insulated 9/16" hollow shaft nut driver, 6" shaft	
	646-5/8-INS	insulated 5/8" hollow shaft nut driver, 6" shaft	-
	33534	Custom heavy-duty Cordura® case	



Cordura® is a registered trademark of INVISTA for durable fabrics.

All dimensions are in inches and (millimeters).

**AWARNING:** Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source. 1000 V

**AWARNING:** Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

**AWARNING:** Do NOT use screwdrivers to pry or chisel

**AWARNING:** Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

AWARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.



# The IA

# Introduction - Screwdrivers, Nut Drivers & Accessories

Klein screwdrivers give professionals extra-quality features that have made the Klein name famous for hand tools – features that assure greater convenience, comfort and efficiency in use, plus exceptional strength and durability.

All Klein drivers are made of the highest quality tempered steel, carefully heat-treated for maximum strength. Shafts have integral flanges that provide an extra-strong, torque-proof anchor in the handle. Strong, durable black tips are forged and precision ground with square edges to fit screw openings securely. They resist slippage and provide positive turning action.

Cushion-Grip screwdrivers feature super-comfortable, sure-grip handles on top-quality blades for the professional. All Klein screwdrivers meet or exceed applicable ANSI and MIL specifications.

# Keystone Cabinet Phillips Square TORX®

# **Using screwdrivers**

The size of the screw and the type of opening it has determines which driver to use. Here are a few tips on how to use a driver that can be of benefit, because screwdrivers are the most often misused and abused hand tools of all.

- Never use a driver to do another tool's job. Using a driver as a pry bar, scraper, or a chisel can ruin the tool, spoil the work and cause injury.
- Never push a driver beyond its capacity.Make a pilot hole for the screw for easier driving.Use square-shank drivers for heavy work.
- Never expose a driver to excessive heat. Direct flame can draw the temper from the metal, weakening and possibly warping it, making it unsafe and inefficient to use.

4. Never use a driver at an angle to the screw. Always keep the shank perpendicular to the screw head. Driving at an angle or using a point that is too small can spoil the screw or slip and damage the work.


Recess

- 5. Never depend on a driver's handle or covered blade to insulate you from electricity. Plastic and Cushion-Grip handles are intended only to provide a firm, comfortable grip. Insulated blades are intended only as a protective measure against shorting out components. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.
- 6. Discard damaged or worn drivers.

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

# **Cushion-Grip Screwdriver Sets**

# Features:



All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT use to pry or chisel.

86

# **Cushion-Grip Screwdriver Sets**

# 8-Piece Cushion-Grip Screwdriver Set

#### Additional Features:

- General purpose selection of the most frequently used screwdrivers.

Include	s one cabin	et-tip, three keystone-tip, fo	ur Phillips-tip style	es.	
Cat. No.	Set Contai	ns			Weight (lbs.)
85078					1.65
	Cat. No.	Description	Shank Length	Overall Length	
	600-1	round-shank, keystone-tip	1-1/2" (38 mm)	3-7/16" (87 mm)	
	601-3	round-shank, #2 Phillips-tip	1-1/2" (38 mm)	3-7/16" (87 mm)	-
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)	-
	602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)	_
	603-1	round-shank, #2 Phillips-tip	1-1/2" (38 mm)	3-7/16" (87 mm)	
	603-3	round-shank, #1 Phillips-tip	3" (76 mm)	6-3/4" (171 mm)	
	603-4	round-shank, #2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)	<b>A</b>
	603-6	round-shank, #3 Phillips-tip	6" (152 mm)	11" (279 mm)	
	* Heavy-du	ıty models			_

# 7-Piece Cushion-Grip Screwdriver Set

# Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes three cabinet-tip, two Phillips-tip and two keystone-tip styles.

Cat. No.	Set Conta	ins			Weight (lbs.)
5076					1.50
	Cat. No.	Description	Blade Length	Overall Length	
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)	
	602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)	
	601-3	round-shank, cabinet-tip	3" (76 mm)	6-3/4" (171 mm)	•
	601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)	•
	605-4	round-shank, cabinet-tip*	4" (102 mm)	8-11/32" (212 mm)	
	603-3	round-shank, #1 Phillips-tip	3" (76 mm)	6-3/4" (171 mm)	
	603-4	round-shank, #2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)	
		uty models	. (************************************		

# 7-Piece Multiple-Application Screwdriver Set

# Additional Features:


- Specialty set for a wide variety of applications.
- Includes two cabinet-tip, one Phillips-tip, two keystone-tip, one rotary and one screw-holding screwdriver.

Cat.No. Set Contains Weight (lbs.)
05077
85077 1.65
Cat. No. Description Blade Length Overall Length
600-4 square-shank, keystone-tip* 4" (102 mm) 8-11/32" (212 mm)
601-6 round-shank, cabinet-tip 6" (152 mm) 9-3/4" (248 mm)
602-6 round-shank, keystone-tip* 6" (152 mm) 10-15/16" (278 mm)
603-4 round-shank, #2 Phillips-tip 4" (102 mm) 8-5/16" (211 mm)
605-6 round-shank, cabinet-tip* 6" (152 mm) 10-11/32" (263 mm)
670-6 cabinet-tip rotary screwdriver 6" (152 mm) 9-3/4" (248 mm)
K36 slotted screw-holding 6" (152 mm) 9-3/4" (248 mm)

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.





# **Cushion-Grip Screwdriver Sets**

# 6-Piece Cushion-Grip Screwdriver Set

#### Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes one cabinet-tip, two keystone-tip and three Phillips-tip styles.

Cat. No.	Set Conta	ins		
85074				
	Cat. No.	Description	Blade Length	Overall Length
	601-3	round-shank, cabinet-tip	3" (76 mm)	6-3/4" (171 mm)
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	600-6	square-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	603-3	round-shank, #1 Phillips-tip	3" (76 mm)	6-3/4" (171 mm)
	603-4	round-shank, #2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
	603-6	round-shank, #3 Phillips-tip	6" (152 mm)	11" (279 mm)
	* Heavy-di	uty models		

1.30





85074

# 5-Piece Cushion-Grip Screwdriver Set

#### Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes two cabinet-tip, one Phillips-tip and two keystone-tip screwdrivers.

85075				
	Cat. No.	Description	Blade Length	Overall Length
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
	602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	603-4	round-shank, #2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
	605-6	round-shank, cabinet-tip*	6" (152 mm)	10-11/32" (263 mm)





# **4-Piece Cushion-Grip Screwdriver Set**

#### Additional Features:

- The screwdrivers Professionals carry most often.
- Includes one Phillips-tip, two keystone-tip, one cabinet-tip screwdrivers.

Cat. No.	Set Contai	ns		
85105				
	Cat. No.	Description	Blade Length	Overall Length
	603-4	round-shank, #2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
	600-6	square-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	* H03///-d1	ity modele		

Heavy-duty models



All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

1.50

88

# **Cushion-Grip Screwdriver Sets**

# **Electronics Screwdrivers**

- Rotating cap for optimum and precise control.
- Klein Cushion-Grip handle for maximum comfort when working on small equipment.
- Professional custom carrying case included in set.
- Screwdrivers sold individually and in set (Cat. No. 85614).

Cat. No.	Set Conta	ins			Weight
85614					.80 lbs. (0.36 kg.)
	Cat. No.	Description	Blade Length	Overall Length	
	614-2	1/16" Slotted	2" (51 mm)	5-1/2" (140 mm)	
	613-3	#0 Phillips	3" (76 mm)	6-1/2" (165 mm)	_
	614-3	3/32" Slotted	3" (76 mm)	6-1/2" (165 mm)	_
	614-4	1/8" Slotted	4" (102 mm)	7-1/2" (191 mm)	_
	614-6	1/8" Slotted	6" (152 mm)	9-1/2" (241 mm)	



# **4-Piece Miniature Cushion-Grip Screwdriver Set**

# Additional Feature:

Precision tips for exact fit and rigorous applications.

Cat. No.	Set Co	Set Contains					
85484						.14	
	Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length		
	604-3	Phillips-tip	#0	3" (76 mm)	5-3/4" (146 mm)		
	606-2	keystone-tip	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)		
	607-3	cabinet-tip	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)		
	608-3	cabinet-tip	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)		



# **5-Piece TORX® Cushion-Grip Screwdriver Set**

#### Additional Features:

- TORX® drive systems transmit more torque to the work and reduce slippage, saving fasteners.
- Chrome-plated shafts resist corrosion.

Cat. No.	Set Conta	Weight (lbs.)				
19555						1.20
	Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length	
	19542	T15	yellow	4" (102 mm)	7-3/4" (197 mm)	
	19543	T20	green	4" (102 mm)	7-3/4" (197 mm)	
	19544	T25	blue	4" (102 mm)	7-3/4" (197 mm)	
	19545	T27	brown	4" (102 mm)	8-5/16" (211 mm)	
	19546	T30	red	4" (102 mm)	8-5/16" (211 mm)	
TORX® is a r	egistered tr	ademark o	f Acument	Intellectual Pro	perties, LLC.	•



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.



# ALE IA

# **Cushion-Grip Screwdriver Sets**

# 2-Piece 10" Long Blade Screwdriver Set

#### Additional Features:

- Phillips-tip is precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Precision-ground narrow cabinet-tip permits blade access where space is limited.
- Ideal for hard-to-reach places where added length is necessary.
- Includes one Phillips-tip and one cabinet-tip.



Cat. No.	Set Contains					Weight (lbs.)
85072						.70
	Cat. No.	Description	Shank Tip Size	Shank Length	Overall Length	
	603-10	round-shank, profilated Phillips-tip	#2	10" (254 mm)	14-5/16" (363 mm)	
	605-10	round-shank, cabinet-tip	1/4" (6 mm)	10" (254 mm)	14-5/16" (363 mm)	

# **4-Piece Square Recess Cushion-Grip Screwdriver Set**

# Additional Features:

- Round shank with square-recess tip.
- Chrome-plated shank for corrosion resistance.
- Works on most combination head receptacle, switch and panel screws.

Cat No.	Set Contains						
85664						1.	
	Cat. No.	Point Size	Color Code	Shank Length	Overall Length		
	660	#0	yellow	4" (102 mm)	7-3/4" (197 mm)	-	
	661	#1	green	4" (102 mm)	7-3/4" (197 mm)	-	
	662	#2	red	4" (102 mm)	8-5/16" (211 mm)	-	
	663	#3	black	4" (102 mm)	8-5/16" (211 mm)	-	



85664

# 2-Piece Stubby Cushion-Grip Screwdriver Set

# Additional Feature:

• Double wings inside handle provide solid, twist-resistant blade anchor.

Cat. No.	Set Conta	nins			Weight (lbs.)
85071					.30
	Cat. No.	Description	Shank Length	Overall Length	
	600-1	round-shank, keystone-tip	1-1/2" (38 mm)	3-7/16" (87 mm)	
	603-1	round-shank, #2 Phillips-tip	1-1/2" (38 mm)	3-7/16" (87 mm)	-



85071

# **Stubby Square-Recess Tip Cushion-Grip Screwdrivers**

#### Additional Features:

- Double wings inside handle provide solid, twist-resistant blade anchor.
- Works on most combination head receptacle and switch screws.
- · Color-coded handle ends for quick and easy identification.

Cat. No.	Set Conta	ins			Weight (lbs.)
85155					.30
	Cat. No.	Description	Shank Length	Overall Length	
	668	round-shank, #1 square-recess tip	1-1/2" (38 mm)	3-7/16" (87 mm)	-
	669	round-shank, #2 square-recess tip	1-1/2" (38 mm)	3-7/16" (87 mm)	-



85155

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

90

# **Cushion-Grip Screwdrivers**

# **Keystone-Tip Screwdrivers - Heavy-Duty Square-Shanks**

#### Additional Features:

- · Heavy-duty square shank for wrench-assisted turning.
- Bolster reinforces shank for hard use.
- Designed for the most demanding uses.



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
600-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
600-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
600-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.65
600-12	1/2" (13 mm)	12" (305 mm)	17-7/16" (443 mm)	.80

# **Keystone-Tip Screwdrivers - Heavy-Duty Round-Shanks**

#### Additional Features:

- Built to handle the tough jobs with ease.
- Hex bolster reinforces shank for hard use and allows wrench assisted turning.

	th air ionne.

602-6

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
600-1*	1/4" (6 mm)	1-1/2" (38 mm)	3-7/16" (87 mm)	.10
602-3	7/32" (6 mm)	3" (76 mm)	6-3/4" (171 mm)	.15
602-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
602-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.35

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
602-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.55
602-10	3/8" (10 mm)	10" (254 mm)	15-7/16" (392 mm)	.60
602-12	3/8" (10 mm)	12" (305 mm)	17-7/16" (443 mm)	.65

<sup>\*</sup> Bolster not available on Cat. No. 600-1 Refer to the Insulated Tools section for insulated screwdrivers.

# Cabinet-Tip Screwdrivers - Round-Shanks

#### Additional Feature:

 Narrow cabinet-tip permits blade access where space is limited.



601-6

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
601-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.10
601-4	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)	.15
601-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.15
601-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
601-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.20

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
Heavy-D	Outy Shanks			
605-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
605-6	1/4" (6 mm)	6" (152 mm)	10-11/32" (263 mm)	.30
605-8	1/4" (6 mm)	8" (203 mm)	12-11/32" (314 mm)	.30
605-10	1/4" (6 mm)	10" (254 mm)	14-11/32" (365 mm)	.35
Refer to	the insulated se	ction for insulated	screwdrivers.	

# Profilated Phillips-Tip Screwdrivers - Round-Shanks

# Additional Features:

 Tips are precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.

Provides accurate fit and torque without slippage.



603-7

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
603-1	#2	1-1/2" (38 mm)	3-7/16" (87 mm)	.10
603-3	#1	3" (76 mm)	6-3/4" (171 mm)	.15
603-4	#2	4" (102 mm)	8-5/16" (211 mm)	.25
603-6	#3	6" (152 mm)	11" (279 mm)	.35

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
603-7	#2	7" (178 mm)	11-5/16" (287 mm)	.30
603-10	#2	10" (254 mm)	14-5/16" (364 mm)	.35

Refer to the insulated section for insulated screwdrivers.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.



# EST. 1857

# **Cushion-Grip Screwdrivers**

# **Electronics Screwdrivers**

#### Additional Feature:

Rotating cap for optimum and precise control.

Cat No.	Tip Type	Tip Size	Shank Length	Overall Length
614-2	Slotted	1/16"	2" (51 mm)	5-1/2" (140 mm)
613-3	Phillips	#0	3" (76 mm)	6-1/2" (165 mm)
614-3	Slotted	3/32"	3" (76 mm)	6-1/2" (165 mm)
614-4	Slotted	1/8"	4" (102 mm)	7-1/2" (191 mm)
614-6	Slotted	1/8"	6" (152 mm)	9-1/2" (241 mm)





614-6

# **Miniature Screwdrivers**

# Additional Feature:

Precision tip for exact fit and rigorous applications.

Cat No.	Tip Type	Tip Size	Shank Length	Overall Length	Weight (lbs.)
604-3	Phillips-tip	#0	3" (76 mm)	5-3/4" (146 mm)	.04
606-2	keystone-tip	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-2	cabinet-tip	3/32" (2.4 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-3	cabinet-tip	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
607-4	cabinet-tip	3/32" (2.4 mm)	4" (102 mm)	6-3/4" (171 mm)	.04
608-2	cabinet-tip	1/8" (3.2 mm)	2" (51 mm)	4-3/4" (121 mm)	.03



Cat No.	Tip Type	Tip Size	Shank Length	Overall Length	Weight (lbs.)
608-3	cabinet-tip	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
608-4	cabinet-tip	1/8" (3.2 mm)	4" (102 mm)	6-3/4" (171 mm)	.05
608-6	cabinet-tip	1/8" (3.2 mm)	6" (152 mm)	8-3/4" (222 mm)	.05
608-8	cabinet-tip	1/8" (3.2 mm)	8" (203 mm)	10-3/4" (273 mm)	.05
608-10	cabinet-tip	1/8" (3.2 mm)	10" (254 mm)	12-3/4" (324 mm)	.05

# **Coated Cabinet-Tip Screwdrivers - Round-Shanks**

# Additional Features:

- Plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
620-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.15
621-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
621-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
621-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.25



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
Heavy-Duty	y Shanks			
620-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.20
620-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40
620-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.60

# Square-Recess Tip Screwdrivers - Round-Shanks

## Additional Features:

- Color-coded handle ends for quick and easy identification.
- Round shank with Square-Recess tip.
- Chrome plated shank for corrosion resistance.

Cat. No.	Tip Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
660	#0	yellow	4" (102 mm)	7-3/4" (197 mm)	.20
661	#1	green	4" (102 mm)	7-3/4" (197 mm)	.20
662	#2	red	4" (102 mm)	8-1/4" (210 mm)	.30
663	#3	black	4" (102 mm)	8-1/4" (210 mm)	.30
665	#1	green	8" (203 mm)	11-3/4" (298 mm)	.30



Cat. No.	Tip Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
666	#2	red	8" (203 mm)	12-1/4" (311 mm)	.40
667	#3	black	8" (203 mm)	12-1/4" (311 mm)	.40
- ·					

Refer to the insulated section for insulated screwdrivers.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

# **Cushion-Grip Screwdrivers**

# TORX® Screwdrivers - Round-Shanks

#### Additional Features:

- Color-coded handle ends for quick and easy identification.
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work.
- Chrome-plated shank for corrosion resistance.

Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
19542	T15	yellow	4" (102 mm)	8-5/16" (211 mm)	.20
19543	T20	green	4" (102 mm)	8-5/16" (211 mm)	.25
19544	T25	blue	4" (102 mm)	8-5/16" (211 mm)	.25



Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
19545	T27	brown	4" (102 mm)	8-5/16" (211 mm)	.25
19546	T30	red	4" (102 mm)	8-5/16" (211 mm)	.25

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

# Rapi-Driv® Screwdrivers

# Rapi-Driv® Screwdrivers


#### Additional Features:

- · Crank-action handle spins screws fast with one hand.
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.

Cat. No.		Tip Type	Tip Size	Shank Length	Overall Length	Weight (lbs.)
670-3		cabinet-tip	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)	.15
670-6		cabinet-tip	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
671-6		cabinet-tip	1/4" (6 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
681-6	•	Phillips-tip	#1	6" (152 mm)	9-3/4" (248 mm)	.20
682-6	•	Phillips-tip	#2	6" (152 mm)	9-3/4" (248 mm)	.25
691-6	0	square-recess	#1	6" (152 mm)	9-3/4" (248 mm)	.35
692-6	0	square-recess	#2	6" (152 mm)	9-3/4" (248 mm)	.35



670-6



# Interchangeable Rapi-Driv®


# Additional Features:

- Interchangeable bit holder allows quick switching between tip styles and works with other standard size bits.
- Crank-action handle allows you to spin screws fast with one hand.
- Blast finish bit provides firm grip on fasteners to reduce cam out.

Cat. No.	Contains	Shaft Length	Overall Length	Weight (lbs.)			
67100	3/16" slotted, #2 Phillips	6" (152 mm)	9-3/4" (248 mm)	.26			
2-in-1 Re	2-in-1 Replacement Bit						
Cat. No.	Fits	Description	Quantity	Weight (lbs.)			



67100



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.



# **Specialty Screwdrivers**

# Demolition Screwdrivers — Keystone-Tip

- Engineered, manufactured and tested for prying and chiseling.
- Plated metal strike cap to protect handle from hammer blows.
- Heat treated metal shaft runs complete length of handle to metal strike cap to transfer metal strike force





Cat. No.	Tip Size	Tip Type	Blade Length	Overall Length	Weight (lbs.)
602-4DD	1/4"	keystone	4" (102 mm)	9" (229 mm)	.37 (0.17 kg.)
602-7DD	5/16"	keystone	7" (178 mm)	12-3/8" (314 mm)	.56 (0.25 kg.)

# 602-4DD

# **Power Conduit Reamer**

- Ream 1/2". 3/4" and 1" conduit and install fittings in a fraction of the time.
- · Reduce time on projects with large quantities of conduit runs.
- Designed to fit into power drill chucks and quick release adapters; impact ready.
- Includes precision engineered replaceable reaming blade.
- Replacement blades are available and the only approved blade for use in our tool.
- Replacement bits are available but any standard 1/4" hex bit will work.

Cat. No.	Conduit Capacity	Weight
85091	conduit reamer drill head for 1/2", 3/4" and 1" conduit	.33 lbs. (0.15 kg.)
19353	conduit reamer replacement blade	.01 lbs. (0.004 kg.)
SQ2115	#2 square recess replacement bit, 15-pack	.01 lbs. (0.004 kg.)



85091

85191





# **Conduit-Fitting and Reaming Screwdriver**

## Additional Features:

- Hooded-blade design keeps tip from slipping out of screws. especially when tightening hard-to-reach conduit fittings.
- Reams and smooths 1/2" (13 mm), 3/4" (19 mm), and 1" (25 mm) thin-wall conduit ends to protect wire and permit correct installation of fittings.
- Reams both the inside and outside of the conduit at the same time.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
85191	5/16" (8 mm)	2-1/2" (64 mm)	7-1/2" (191 mm)	.50
19353	conduit reamer	replacement blade kit		.01





# **Conduit Reamer**

- Locks onto screwdrivers: reams and smooths thin-wall conduit.
- · Reams ID and OD at the same time.
- Two set-screws for round- and square-shank screwdrivers.
- Fits up to 3/8" (10 mm) keystone-tip screwdrivers.
- NOT for use on power tools.

Cat. No.	Conduit Capacity	Weight (lbs.)
19352	1/2", 3/4", 1"	.20
19353	conduit reamer replacement blade kit for 19352	.01
19351	conduit reamer replacement blade for 19350	.01



19352

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

AWARNING: Do NOT use to pry or chisel.




# **Specialty Screwdrivers**

# **Screw-Holding Screwdrivers**

#### Additional Features:

 Starts and drives screws with one hand when working in hard-to-reach spaces.







32	22	1	b

612-4

Cat. No.	Screwdriver Type	Shank Length	Overall Length	Weight (lbs.)
32215	1/4" cabinet	7" (178 mm)	11-1/4" (276 mm)	0.32
32216	#2 Phillips	7" (178 mm)	11-1/4" (276 mm)	0.32

# **Terminal Block Screwdriver**

#### Additional Features:

- Precision-machined tip provides exact fit for terminal block screws.
- Tip is up to 19% stronger than competitors.
- Tip provides 76% higher torque value than the required ASME B107 Standard.
- Cushion-Grip handle offers greater torque comfort.

Cat. No.	Shank Top Width	Shank Length	Overall Length	Weight (lbs.)
612-4	1/8" (3.2 mm)	4" (100 mm)	7-3/4" (200 mm)	0.15

# Wire Bending Cabinet-Tip Screwdrivers - Round-Shanks

#### Additional Feature:

 Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.



605-6B

Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
605-4B	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	Nos. 10, 12, 14	chrome-plated	0.25
605-6B	1/4" (6 mm)	6" (152 mm)	10-11/32" (263 mm)	Nos. 10, 12, 14	chrome-plated	0.30



# Wire Bending Phillips-Tip Screwdrivers - Round-Shanks

# Additional Feature:

 Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.



603-4B

Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
603-3B	#1	3" (76 mm)	6-3/4" (171 mm)	Nos. 12 and 14	chrome-plated	0.15
603-4B	#2	4" (102 mm)	8-5/16" (211 mm)	Nos. 10, 12, 14	chrome-plated	0.25



# Wire Bending Square-Recess Tip Screwdrivers - Round Shanks

#### Additional Feature:

 Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.



Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
661B	#1	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.20
662B	#2	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.30





661B

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.



# **Multi-Bit Screwdrivers/Nut Drivers**

# Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Superior torque for tough applications.
- Interchangeable shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver
- Strong, heat-treated nut drivers for improved torque.

Cat. No.	Shaft Length	Overall Length	Weight	
32557	2.95" (75 mm)	7.9" (201 mm)	0.48	



32557

		•	<b>(1)</b>	0	0	0	0	0	
3/16"	1/4"	#1	#2	1/4"	5/16"	3/8"	#1	#2	3/8"

# **Ratcheting Multi-Bit Screwdriver/Nut Driver**

- High-torque ratcheting mechanism for tough applications.
- Shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver.
- Strong, heat-treated nut drivers for improved torque.
- 3-way ratcheting mechanism for forward, reverse and locked positions.

Cat. No.	Shaft Length	Overall Length	Weight
32558	2.95" (75 mm)	8.0" (203 mm)	0.71



32558

		<b>①</b>	<b>①</b>	0	0	0	0	0	
3/16"	1/4"	#1	#2	1/4"	5/16"	3/8"	#1	#2	3/8"

# Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Interchangeable shaft holds 4 universal tips and converts to 2 nut driver sizes.
- Extended shafts and blades provide 39% longer reach.
- Shaft holds 4 universal tips and converts to 2 nut driver sizes.
- Small diameter shaft for comfortable grip and quick,

casy turi	iiig.		
Cat. No.	Shaft Length	Overall Length	Weight
32559	4.11" (104 mm)	9.1" (231 mm)	0.41



32559

Cat No. 32560 Cat. No. 32559

Cat. No.	Shaft Length	Overall Length	Weight		Δ	$\bigcirc$		$\cap$	$\mathbf{\cap}$				4	$\bigcirc$	(
32559	4.11" (104 mm)	9.1" (231 mm)	0.41	1/4"	#0	1/4"	5/16"	#1	<u> </u>	3/16"	1/4"	#1	#2	1/4"	
32560	4.11" (104 mm)	9.1" (231 mm)	0.41	- 1/4	#2	1/4	5/10	# I	#4	3/10	1/4	n I	<i>" L</i>	1/7	

# Stubby Multi-Bit Screwdriver/Nut Driver

- Compact design features standard 1-1/4" shaft allowing easy access to tight work spaces
- Shaft holds 4 universal tips and converts to 2 nut driver sizes.

Cat. No.	Shaft Length	Overall Length	Weight
32561	1.27" (32 mm)	3.2" (81 mm)	0.16 lbs. (0.07 kg.)
32562	1.27" (32 mm)	3.2" (81 mm)	0.16 lbs. (0.07 kg.)



32561

Cat. No.	Shaft Length	Overall Length	Weight	Cat. No. 32561	Cat No. 32562
32561	1.27" (32 mm)	3.2" (81 mm)	0.16 lbs. (0.07 kg.)		<b>=0</b> 0000
32562	1.27" (32 mm)	3.2" (81 mm)	0.16 lbs. (0.07 kg.)	_ 3/16" 1/4" #1 #2 1/4" 5/16"	3/16" #2 1/4" 5/16" #1 #2

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

# **Multi-Bit Screwdrivers/Nut Drivers**

# 5-in-1 Screwdriver/Nut Driver

• End of handle is marked to quickly identify tool.



Cat. No.	Contains	Weight (lbs.)
32476	5/16" nut driver, #1 and #2 Phillips, 9/32" slotted and 3/16" slotted	.35

# 10-in-1 Screwdriver/Nut Driver

• End of handle is marked to quickly identify tool.



Cat. No.	Contains	Weight (lbs.)
32477	5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess	.35

# 11-in-1 Screwdriver/Nut Driver

- Integrated screwdriver/nut driver shaft holds
   8 popular tips and converts to 3 nut driver sizes.
- End of handle is marked to quickly identify tool.



TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Cat. No.	Contains	Weight (lbs.)
32500	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess	.44

# 11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/ Installation Bit

- Includes unique style bit for installation/removal of common TR-4 Schrader<sup>®</sup> valves and aggressive thread extractor tip for backing out broken cores.
- Great for HVAC and other industrial applications.



Cat. No.	Contains	Weight (lbs.)
32527	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, #1 square and #2 square, 1/4" and 3/16" slotted, Schrader® valve core removal/installation – extractor	.44

Schrader® is a registered trademark of Schrader International, Inc.

# 10-in-1 Folding Screwdriver/Nut Driver

- Conveniently folds up for easy storage or to fit into your pocket.
- Each driver arm contains four interchangeable bit styles and two nut drivers.
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners.
- The quick release button easily unlocks a fully extended driver arm.











TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Cat. No.	Handle Color	Description	Weight (lbs.)
32534	blue	5/16" & 1/4" nut drivers, #1 and #2 Phillips, 1/4" & 3/16" slotted, #1 and #2 square-recess, and Schrader <sup>®</sup> valve core removal/installation – extractor	0.37
32535	black	5/16" & 1/4" nut drivers, #1 and #2 Phillips, 1/4" & 3/16" slotted, T10 & T15 TORX®, and #1 and #2 square-recess	0.37
32536	green	5/16" & 1/4" nut drivers, T6, T7, T8, T10, T15, T20, T25, T27 TORX®	0.37
32537	green	5/16" & 1/4" nut drivers, T7, T8, T9, T10, T15, T20, T25, T27 TORX®	0.37
32538	red	5/16" & 1/4" nut drivers, 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16" standard hex	0.37
32539	blue	5/16" & 1/4" nut drivers, .9 mm, 1.3 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm metric hex	0.37



# Replacement Parts Multi-Bit Screwdriver/Nut Drivers

# Replacement Bits for Screwdriver/Nut Drivers

 Precision-machined tips for exact fit into fastener.







Replacement	Bits for Multi-Bit Interchangeable	Screwdriver/Nut Drivers (32557, 32558, 32559, 32560, 325	61)
Cat. No.	Fits	Description	Quantity
32392	32557 and 32558	Heavy Duty Main Blade Barrel	contains 1 unit
32394	32557 and 32558	Heavy Duty Secondary Blade Barrel	contains 2 units
32395	32559 and 32560	Extended Blade Barrel	contains 1 unit
32396	32561	Stubby Blade Barrel	contains 1 unit
32397	32557 and 32558	Screwdriver Bit & #2 PH x #1 Square	contains 2 bits
32398	32557, 32558 and 32561	Screwdriver Bit & #1 PH x 1/4 Slotted	contains 2 bits
32399	32557 and 32558	Screwdriver Bit & #2 Square x 3/16 Slotted	contains 2 bits
32400	32559	Extended Screwdriver Bit & #2 PH x #1 PH	contains 2 bits
32401	32559	Extended Screwdriver Bit & 3/16 Slotted x 1/4 Slotted	contains 2 bits
32410	32560	Extended Screwdriver Bit & #2 Square x #2 PH	contains 2 bits
32411	32560	Extended Screwdriver Bit & #1 Square x 1/4 Slotted	contains 2 bits
32412	32561	Screwdriver Bit & #2 PH x 3/16 Slotted	contains 2 bits

Replacement Bits for 5-in-1 Interchangeable Screwdriver/Nut Drivers					
Cat. No.	Fits	Description	Quantity		
32478	5-in-1 (Cat. No. 32476)	#1 Phillips – 3/16" slotted	contains 1 bit		
32479	5-in-1 (Cat. No. 32476)	#2 Phillips – 9/32" slotted	contains 1 bit		

Replacement	Bits for 10-in-1, 11-in-1 and 10-Fold	® Interchangeable Screwdriver/Nut Drivers		
Cat. No.	Fits	Description	Quantity	
32482	10-in-1, 11-in-1 and 10-Fold™	#1 Phillips & 3/16" Slotted	contains 2 bits	
32483	10-in-1, 11-in-1 and 10-Fold™	#2 Phillips & 1/4" Slotted	contains 2 bits	
32484	10-in-1, 11-in-1 and 10-Fold™	#1 Square & #2 Square	contains 2 bits	
67101	10-in-1, 11-in-1 and 10-Fold™	#2 Phillips & 3/16" Slotted	contains 2 bits	
32540	10-in-1, 11-in-1 and 10-Fold™	TT7 & TT8 Tamperproof TORX®	contains 2 bits	
32541	10-in-1, 11-in-1 and 10-Fold™	TT9 & TT10 Tamperproof TORX®	contains 2 bits	
32542	10-in-1, 11-in-1 and 10-Fold™	TT15 & TT20 Tamperproof TORX®	contains 2 bits	
32543	10-in-1, 11-in-1 and 10-Fold™	TT25 & TT27 Tamperproof TORX®	contains 2 bits	
32544	10-in-1, 11-in-1 and 10-Fold™	#6 TORX® & #7 TORX®	contains 2 bits	
32485	10-in-1, 11-in-1 and 10-Fold™	#10 TORX® & #15 TORX®	contains 2 bits	
32545	10-in-1, 11-in-1 and 10-Fold™	#T8 TORX® & #10 TORX®	contains 2 bits	
32546	10-in-1, 11-in-1 and 10-Fold™	#T25 TORX® & #T27 TORX®	contains 2 bits	
32547	10-in-1, 11-in-1 and 10-Fold™	3/32" Hex & 7/64" Hex	contains 2 bits	
32548	10-in-1, 11-in-1 and 10-Fold™	5/32" Hex & 3/16" Hex	contains 2 bits	
32549	10-in-1, 11-in-1 and 10-Fold™	1/16" Hex & 5/64" Hex	contains 2 bits	
32550	10-in-1, 11-in-1 and 10-Fold™	1/8" Hex & 9/64" Hex	contains 2 bits	
32551	10-in-1, 11-in-1 and 10-Fold™	.9 mm Hex & 1.3 mm Hex	contains 2 bits	
32552	10-in-1, 11-in-1 and 10-Fold™	1.5 mm Hex & 2 mm Hex	contains 2 bits	
32553	10-in-1, 11-in-1 and 10-Fold™	2.5 mm Hex & 3 mm Hex	contains 2 bits	
32554	10-in-1, 11-in-1 and 10-Fold™	4 mm Hex & 5 mm Hex	contains 2 bits	

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Always wear approved eye protection.

32510

# **Multi-Bit Screwdrivers/Nut Drivers**

# **Non-Ratcheting Magnetic Screwdriver** with 32-Piece Tamperproof Bit Set

- Cushion-Grip handle for superior torque and comfort.
- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use.
- Includes complete tamperproof bit set in block.

Cat. No.	Set Contains	Weight (lbs.)
32510		.71
	Bits Included	
	TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40	
	Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"	
	Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm	
	Spanner – 4, 6, 8, and 10	
	Tri-Wing <sup>®</sup> $-1$ , 2, 3 and 4	
	TORQ-SET® – 6, 8 and 10	
	1/4" square to 1/4" hex adapter to drive sockets	

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.



- Durable PVC black block allows for easy storage of standard bits.
- Block slides over most screwdriver shafts for easy bit access and storage.
- Industrial strength, heat-treated steel bits for long lasting use.

# **32-Piece Standard Tip Bit Set**



Cat. No.	Set Contains	Weight (lbs.)
32526		.425
	Bits Included	
	Hex - 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" and 3/16"	•
	Phillips – #0, #1, #2 (Qty. 3), and #3	
	Square Recess – #1, #2, and #3	
	TORX® - T6, T7, T8, T10, T15, T20 and T25	
	Slotted – 3-4, 5-6, 6-8, 8-10, 10-12, 12-14 screw sizes	
	Clutch - 5/32" and 3/16"	
	1/4" square to 1/4" hex adapter to drive sockets	-

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

# **32-Piece Tamperproof Tip Bit Set**



Cat. No.	Set Contains	Weight (lbs.)
32525		.425
	Bits Included	
	TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40	-
	Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"	_
	Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm	_
	Spanner – 4, 6, 8, and 10	_
	Tri-Wing® - 1, 2, 3 and 4	_
	TORQ-SET® – 6, 8 and 10	_
	1/4" square to 1/4" hex adapter to drive sockets	

All dimensions are in inches and (millimeters).


**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.





# Features:



# 5-Piece Journeyman™ Screwdriver Set

# Additional Features:

 General purpose selection of the most frequently used screwdrivers.

Cat. No.	Set Cont	ains			V
JSDS01					1.
	Cat. No.	Description	Shaft Length	Overall Length	
	JSD6C06	3/16" cabinet-tip	6" (152 mm)	10-1/4" (260 mm)	
	JSD4K08	1/4" keystone-tip	4" (102 mm)	9" (228 mm)	-
	JSD6K09	5/16" keystone-tip	6" (152 mm)	11" (279 mm)	
	JSD4PH1	#1 Phillips-tip	4" (102 mm)	8-1/4" (210 mm)	•
	JSD4PH2	#2 Phillips-tip	4" (102 mm)	9" (228 mm)	-
					-







All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

100

# ogrewuriyers, Nut Drivers

# **7-Piece Journeyman™ Screwdriver Set**

#### Additional Features:

JSDS02

Accommodates a broad range of standard fastener sizes.





Set Colle	ailis			weigiii
				1.65
Cat. No.	Description	Shaft Length	Overall Length	
JSD4C06	3/16" cabinet-tip	4" (102 mm)	8-1/4" (210 mm)	
JSD6C06	3/16" cabinet-tip	6" (152 mm)	10-1/4" (260 mm)	
JSD4K08	1/4" keystone-tip	4" (102 mm)	9" (228 mm)	
JSD6K09	5/16" keystone-tip	6" (152 mm)	11" (279 mm)	
JSD4PH1	#1 Phillips-tip	4" (102 mm)	8-1/4" (210 mm)	
JSD4PH2	#2 Phillips-tip	4" (102 mm)	9" (228 mm)	
JSD6PH3	#3 Phillips-tip	6" (152 mm)	11" (279 mm)	



JSDS02

# **Journeyman™ Screwdrivers**

# Journeyman™ Cabinet-Tip Screwdrivers - Round Shaft

#### Additional Features:

- Narrow cabinet-tip permits blade access where space is limited.
- Exceptionally hard steel shaft efficiently transfers torque into the tip.



JSD6C06

Cat. No.	Shaft Tip Width	Shaft Length	Overall Length	Weight (lbs.)
JSD4C06	3/16" (5 mm)	4" (102 mm)	8-1/4" (210 mm)	0.15
JSD6C06	3/16" (5 mm)	6" (152 mm)	10-1/4" (260 mm)	0.15



# Journeyman™ Phillips-Tip Screwdrivers - Round Shaft

# Additional Features:

- Tips are precision machined to provide a consistent symmetry.
- Provides accurate fit and torque without slippage.



JSD4PH2

Cat. No.	Tip Size	Shaft Length	Overall Length	Weight (lbs.)
JSD4PH1	#1	4" (102 mm)	8-1/4" (210 mm)	0.15
JSD4PH2	#2	4" (102 mm)	9" (228 mm)	0.25
JSD6PH3	#3	6" (152 mm)	11" (279 mm)	0.35



#### Additional Features:

- The most popular flat tip style used in high torque applications.
- Hex bolster reinforces blade for hard use and shows for wrench assisted turning.



JSD6K09

Cat. No.	Shaft Tip Width	Shaft Length	Overall Length	Weight (lbs.)
JSD4K08	1/4" (6 mm)	4" (102 mm)	9" (228 mm)	0.25
JSD6K09	5/16" (8 mm)	6" (152 mm)	11" (279 mm)	0.35



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.




# **Plastic-Handle Screwdriver Set**

# **Features:**

Meets or exceeds applicable ASME / ANSI specifications.

Smooth Comfordome® handles fit the palm of the hand comfortably.



# 7-Piece Combination Screwdriver Set

#### Additional Features:

 Set contains two Phillips-tip screwdrivers, two slotted keystone-tip screwdrivers and three popular cabinet-tip screwdrivers.

Cat. No.	Set Conta	ins		
85276				
	Cat. No.	Description	Shank Length	Г
	BD111	#1 Phillips-tip	3" (76 mm)	_
	BD122	#2 Phillips-tip	4" (102 mm)	_
	BD284	1/4" square-shank, keystone-tip	4" (102 mm)	_
	BD306	5/16" square-shank, keystone-tip	6" (152 mm)	_
	A216-3	1/8" round-shank, cabinet-tip	3" (76 mm)	_
	A216-4	1/8" round-shank, cabinet-tip	4" (102 mm)	_
	A216-6	1/8" round-shank, cabinet-tip	6" (152 mm)	_



# **Pocket-Clip Screwdrivers**

#### Additional Features:

- Round-shank screwdrivers ranging from 3-1/4" (82 mm) to 6-7/16" (164 mm) long.
- Convenient pocket clip.
- Cat. No. A010 has keystone-tip, Cat. No. P12 has Phillips-tip, and all others have cabinet-tip.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
Keystone	e-Tip and Cabino	et-Tip, Pocket-l	Clip Screwdrivers	
A010	3/32" (2.4 mm)	1-3/8" (35 mm)	3-1/4" (82 mm)	.03
A130-2	1/8" (3.2 mm)	2" (51 mm)	3-7/8" (98 mm)	.05
A130-3	1/8" (3.2 mm)	3" (76 mm)	4-7/8" (124 mm)	.04
A116-2	3/32" ( 2.4 mm)	2" (51 mm)	4-7/16" (113 mm)	.05
A116-3	3/32" ( 2.4 mm)	3" (76 mm)	5-7/16" (138 mm)	.03
A116-4	3/32" ( 2.4 mm)	4" (102 mm)	6-7/16" (164 mm)	.03
A131-2	1/8" ( 3.2 mm)	2" (51 mm)	4-7/16" (113 mm)	.05



A116-4

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

102

# **Plastic-Handle Screwdrivers**

# **Midget Screwdriver**

#### Additional Features:

- Specially designed for delicate instrument work.
- Keystone-tip screwdriver.



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
A000	3/32" (2 mm)	1-1/2" (38 mm)	2-7/8" (73 mm)	.02

C718

3/8" (9.5 mm)

# **Keystone-Tip Screwdrivers – Square-Shanks**

#### Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
BD284	1/4" (6.3 mm)	4" (102 mm)	8-1/2" (216 mm)	.25
BD286	1/4" (6.3 mm)	6" (152 mm)	10-1/2" (267 mm)	.30
BD306	5/16" (7.9 mm)	6" (152 mm)	11-3/16" (284 mm)	.35
BD308	5/16" (7.9 mm)	8" (203 mm)	13-3/16" (335 mm)	.40



23-5/16" (592 mm)

.95

BD156

A216-6

18" (457 mm)

# **Keystone-Tip Screwdrivers – Round-Shanks**

#### Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
BD143	7/32" (5.6 mm)	3" (76 mm)	7-1/2" (190 mm)	.20
BD144	1/4" (6.3 mm)	4" (102 mm)	8-1/2" (216 mm)	.25
BD146	1/4" (6.3 mm)	6" (152 mm)	10-1/2" (267 mm)	.25
BD156	5/16" (7.9 mm)	6" (152 mm)	11-3/16" (284 mm)	.35




# Cabinet-Tip Screwdrivers - Round-Shanks

# Additional Features:

- Small-diameter shank for use in recessed holes or tight places.
- Well-suited for electrical and telecommunications work.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
A216-2	1/8" (3.2 mm)	2" (51 mm)	5" (127 mm)	.05
A216-3	1/8" (3.2 mm)	3" (76 mm)	6" (152 mm)	.05
A216-4	1/8" (3.2 mm)	4" (102 mm)	7" (178 mm)	.05
A216-6	1/8" (3.2 mm)	6" (152 mm)	9" (228 mm)	.05
A216-8	1/8" (3.2 mm)	8" (203 mm)	11" (279 mm)	.05
A216-10	1/8" (3.2 mm)	10" (254 mm)	13" (330 mm)	.05



#### A316-3 A316-4 A316-6 A316-8 10" (254 mm) A316-10 3/16" (4.8 mm) 13-5/8" (346 mm) .20

# Profilated Phillips-Tip Screwdrivers - Round-Shanks

# Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
BD111	#1	3" (76 mm)	6-5/8" (168 mm)	.10
BD122	#2	4" (102 mm)	8-1/2" (216 mm)	.20
BD133	#3	6" (152 mm)	11-3/16" (284 mm)	.35
P18	#1	8" (203 mm)	11-1/2" (292 mm)	.15

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
P28	#2	8" (203 mm)	11-5/8" (295 mm)	.20
P212	#2	12" (305 mm)	15-5/8" (397 mm)	.25
P202	#2	20" (508 mm)	24-1/2" (622 mm)	.55

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.







# **Specialty Plastic-Handle Screwdrivers**

# **Magnetic Screwdriver Set**

- Each screwdriver has a powerful magnet built into its shank to hold interchangeable bits and also screws.
- Comfortable handle for easier driving.
- Interchangeable bits store inside handle for quick access.
- Wide selection of bits for different screw types.

Cat. No.	Bits Included	Shank Length with Bits	Overall Length	Weight (lbs.)
70035	3/16" and 9/32" slotted and #1 and #2 Phillips	3-3/4" (95 mm)	7-1/4" (184 mm)	.25

# **Ratcheting Screwdriver Set**

- Slotted and Phillips-tip set.
- Contains a unique 3-position ratcheting screwdriver plus an assortment of blade types and/or sizes.

	the bits store inside the handle for quick access.	-	-	
Cat. No.	Bits Included	Shank Length with Bits	Overall Length	Weight (lbs.)
32473	3/16" and 9/32" slotted plus #1 and #2 Philling	4-1/4" (108 mm)	8-3/4" (222 mm)	40

# **Screwdriver Replacement Bits**

- These precision-milled bits are 1" in length and are 1/4" hex.
- Fits replaceable-bit screwdrivers and other sockets that accept 1/4" hex bits.

Cat. No.	Bit Type	Tip Size	Weight (lbs.)
4HS316	slotted	3/16"	.02
4HS932	slotted	9/32"	.02
4H1P2	Phillips	#2	.02
4H1R1	square-recess	#1	.01
4H1R2	square-recess	#2	.01
4H1R3	square-recess	#3	.01
4HT15	TORX®	T15	.02
4HT20	TORX®	T20	.01
4HT25	TORX®	T25	.02
4HT27	TORX®	T27	.02



70035

32473

Cat. No.	Bit Type	Tip Size	Weight (lbs.)
4HT30	TORX®	T30	.02

Cat. No.		Weight (lbs.)
Bit Sets	Bit Selection	
70036	3/16", 9/32" slotted plus #1 and #2 Phillips tips	.05
70283	#1, #2, #3 square-recess tips	.05
70432	T15, T20, T25, T27, T30 TORX® tips	.05
TORX® is	a registered trademark of Acument Intellectual	Properties, LLC.

# 4-in-1 Screwdriver

- Versatile screwdriver with interchangeable, snap-in blades.
- Tool supplied with four different tips on two reversible blades.

Cat. No.	Description	Overall Length	Weight (lbs.)
32460	screwdriver with two dual-tipped blades	7-5/8" (194 mm)	.370
32478	#1 Phillips & 3/16" slotted	-	.036
32479	#2 Phillips & 9/32" slotted	-	.044



# **3-Piece Slotted Screw-Holding Screwdriver Set**

Not designed for torquing or tightening.

Cat. No.	Set Contain	S	Weight (lbs.)	
SK234			.40	
	Cat. No.	Shank Size		
	K23	3/16" x 3" (5 mm x 76 mm)		
	K34	1/4" x 4" (6.3 mm x 102 mm)		
	K46	5/16" x 6" (8 mm x 152 mm)		

All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

104

# **Specialty Plastic-Handle Screwdrivers**

# **Slotted Screw-Holding Screwdrivers**

- Split-blade screw-holding driver wedges into screw slot.
- · Positive gripping action holds, starts, and drives slotted screws in awkward, hard-to-reach places.
- Not designed for torquing or tightening.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
K21†	1/16" (1.6 mm)	3" (76 mm)	5-1/4" (133 mm)	.05
K23	3/16" (5 mm)	3" (76 mm)	5-1/4" (133 mm)	.05
K28	3/16" (5 mm)	8" (203 mm)	10-1/4" (260 mm)	.10
K34‡	1/4" (6.3 mm)	4" (102 mm)	7-3/4" (197 mm)	.10
K36‡	1/4" (6.3 mm)	6" (152 mm)	9-3/4" (247 mm)	.15



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
K38‡	1/4" (6.3 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
K44	5/16" (8 mm)	4" (102 mm)	8-1/4" (209 mm)	.25
K46	5/16" (8 mm)	6" (152 mm)	10-1/4" (260 mm)	.25
K48	5/16" (8 mm)	8" (203 mm)	12-1/4" ( 311 mm)	.30

† Precision blade for use with small precision screws. Blade thickness of .028" expanding to .045". ‡ Blade thickness of .043" expanding to .085". Note: K21 and K23 have pocket clips.

# **Screw-Holding Screwdrivers**

# Phillips-Tip Screw-Holding Screwdrivers

- Blade separates to hold the fastener.
- Positive gripping action holds and starts Phillips screws in awkward, hard-to-reach places.
- Not designed for torquing or tightening.

Cat. No.	Overall Length	Weight (lbs.)
K14	5" (127 mm) with pocket clip	.05
K16	7" (178 mm)	.05
K19	9" (229 mm)	.05




# **Offset Screwdrivers**

# **Slotted-Tip Offset Screwdrivers**

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	For Screw Nos.	Overall Length	Tip Width	Weight (lbs.)
V01	2 to 6	3" (76 mm)	3/16" (5 mm)	.01
V02	6 to 10	4-1/4" (108 mm)	1/4" (6.3 mm)	.05
V03	8 to 12	5" (127 mm)	5/16" (8 mm)	.11
V04	12 to 16	6" (152 mm)	3/8" (9.5 mm)	.25



# Phillips-Tip Offset Screwdrivers

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	Point Nos.	Overall Length	Weight (lbs.)
P120	#1 and #2	4-3/4" (121 mm)	.05
P340	#3 and #4	6" (152 mm)	.20



# **Combination-Tip Offset Screwdriver**

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	For Screw Nos.	Overall Length	Tip Width	Weight (lbs.)
V05	1/4" slotted #2 Phillips	5" (127 mm)	1/4" (6.3 mm)	.05



All dimensions are in inches and (millimeters).

AWARNING: NOT insulated. Will NOT protect against electrical shock.

AWARNING: Do NOT use to pry or chisel.






# **Offset Screwdrivers**

# 2-Piece Offset Screwdriver Set

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	Set Contains	Weight (lbs.)
210122	P120 (No. 1 and No. 2 Phillips-tip) and V02 (1/4" to 5/16" slotted tip)	.10



# **Specialty Driver Set**

# **Reversible Impact-Driver Set**

- Rugged, hand-impact driver turns rusted, frozen, or other stubborn screws.
- Can also be used with 3/8" square-drive impact sockets.
- Internal, spring-loaded, helical design transforms the impact of a hammer blow to up to 200 ft.-lbs. of shock torque.
- · Easily reverses for tightening or loosening screws.
- Constructed of high-grade alloy steel that has been heat-treated for added strength.
- · Reclosable, seal-tight vinyl pouch with hang-up grommet.



2.15
l pouch .25
/

# **Torque Screwdrivers**

# **Torque-Screwdriver Set**

- Compact, easy to use set.
- Form-fitted storage box to keep set organized.

Cat. No.	Contains	Weight (lbs.)
57034	torque screwdriver Cat. No. 57035, 8-piece bit set Cat. No. 57036, rugged form-fitted storage box	1.0



# **Torque Screwdriver**

- Adjustable, torque-limiting screwdriver with calibrated micrometer scale.
- Torqued to micrometer accuracy. Accurate to ±6° plus 1/2 graduation.
- Graduated in 2 in.-lbs. (.2 NM) increments.
- Torques either clockwise or counter-clockwise.
- Can be preset and sealed for production use.
- Meets MIL-H26497 specifications.
- Easy-release bit holder. Bits are held securely during operation, yet are easily removed when released.
- Aluminum outside construction for light weight and non-magnetic characteristics.
- Non-slip grip.
- Bits not included.

Cat. No.	Range	Drive Size	Overall Length	Weight (lbs.)
57035	2-36 inlb.	1/4" female	8" (203 mm)	.50

57035

57036

# 8-Piece Torque-Screwdriver Bits Set

• Set of eight bits for Cat. No. 57035 torque screwdriver.



Cat. No.	Contains	Weight (lbs.)
57036	Phillips No. 1 and No. 2; slotted No. 4 (3/16" x .034"), No. 5 (7/32" x .036"), No. 6 (1/4" x .038"), No. 10 (5/16" x .046"), No. 12 (3/8" x .050"); 1/4" hex-to-square male adapter	.50

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: Never use on or near live electrical circuits.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

106

# **Cushion-Grip Nut Driver Sets**

# Features:



# 7-Piece Cushion-Grip Nut Driver Set — 3" Shafts


 Set contains 630-3/16, 630-1/4, 630-5/16, 630-11/32, 630-3/8. 630-7/16, and 630-1/2. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
631	1.50

# 7-Piece Hollow-Shaft\* Magnetic Tip Cushion-Grip Nut Driver Set — 3" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 630-3/16M, 630-1/4M, 630-5/16M, 630-11/32M, 630-3/8M, 630-7/16M, and 630-1/2M. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
631M	1.50
*3/16" magnetic nut driver does not have hollow shaft	



# 7-Piece Cushion-Grip Nut Driver Set — 6" Shafts

 Set contains 646-3/16, 646-1/4, 646-5/16, 646-11/32, 646-3/8, 646-7/16, and 646-1/2. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)	
647	1.55	O

# 7-Piece Cushion-Grip Hollow-Shaft\* Magnetic Tip Nut Driver Set — 6" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 646-3/16M. 646-1/4M, 646-5/16M, 646-11/32M, 646-3/8M, 646-7/16M, 646-1/2M. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
647M	1.55
*2/16" magnetic put driver does not have hellow shoft	







631M

'3/16" magnetic nut driver does not have hollow shaft

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.



## **Cushion-Grip Nut Driver Sets**

## **4-Piece Cushion-Grip Nut Driver Set**

### Additional Features:

• Set contains: 630-1/4, 630-5/16, 630-3/8, 630-9/16. (See individual tool listings for more details.)

Cat. No.	Set Contail	18				W
633						1.
	Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	
	630-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	
	630-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	-
	630-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	-
	630-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)	-



## 2-Piece Cushion-Grip Stubby Nut Driver Set — 1-1/2" Shafts

### Additional Features:

- Full hollow shaft for long bolts or studs.
- Stubby nut drivers allow for work in close guarters.
- Cat. No. 610M features magnetic tips.

.30



Cat. No.	Set Conta	ins				
610						
	Cat. No.	Color	Hex	Shaft	Overall	

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length
610-1/4	red	1/4"	1-1/2" (38 mm)	3-1/2" (89 mm)
610-5/16	yellow	5/16"	1-1/2" (38 mm)	3-1/2" (89 mm)

Cat. No.	Set Contains
610M	

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length
610-1/4M	red	1/4"	1-1/2" (38 mm)	3-1/2" (89 mm)
610-5/16M	yellow	5/16"	1-1/2" (38 mm)	3-1/2" (89 mm)

## 2-Piece Magnetic Tip Cushion-Grip Nut Driver Sets

## Additional Features:

• General purpose selection of the most frequently used nut drivers. (See individual tool listings for more details).

Cat. No.	Set Contains	Weight (lbs.)
630M	630-1/4M, 630-5/16M	.40
646M	646-1/4M, 646-5/16M	.50





630M

## 7-Piece Metric Cushion-Grip Nut Driver Set — 3" Shafts

### Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Set Contair	18				Weight (lbs.)
65160						1.50
	Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length	
	630-5mm	black	5 mm	3" (76 mm)	6-3/4" (171 mm)	
	630-5.5mm	brown	5.5 mm	3" (76 mm)	6-3/4" (171 mm)	
	630-6mm	red	6 mm	3" (76 mm)	6-3/4" (171 mm)	-
	630-7mm	orange	7 mm	3" (76 mm)	6-3/4" (171 mm)	-
	630-8mm	yellow	8 mm	3" (76 mm)	6-3/4" (171 mm)	-
	630-9mm	green	9 mm	3" (76 mm)	6-3/4" (171 mm)	
	630-10mm	blue	10 mm	3" (76 mm)	6-3/4" (171 mm)	0



65160

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

## **Cushion-Grip Nut Drivers**

## Cushion-Grip Stubby Nut Drivers — 1-1/2" Shafts

### Additional Features:

- Full hollow shaft for long bolts or studs.
- Stubby nut drivers allow for work in close quarters.
- Meets or exceeds applicable ASME / ANSI specifications.





610-5/16

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
610-1/4	red	1/4"	1-1/2" (38 mm)	3-1/2" (89 mm)	.10
610-5/16	yellow	5/16"	1-1/2" (38 mm)	3-1/2" (89 mm)	.10

## Cushion-Grip Hollow-Shaft Nut Drivers — 3" Shafts



### Additional Features:

630-1/2

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
630-3/16	black	3/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	.20
630-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-11/32	green	11/32"	3" (76 mm)	6-3/4" (171 mm)	.20
630-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	.20
630-7/16	brown	7/16"	3" (76 mm)	7-5/16" (186 mm)	.25
630-1/2	red	1/2"	3" (76 mm)	7-5/16" (186 mm)	.25
630-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)	.35
630-5/8	yellow	5/8"	4" (102 mm)	9-3/8" (238 mm)	.35

Refer to the insulated section for insulated nut drivers.

## Metric Cushion-Grip Hollow-Shaft Nut Drivers — 3" Shafts



### Additional Features:

630-11mm

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length	Weight (lbs.)
630-4mm	red	4 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-4.5mm	yellow	4.5 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-5mm	black	5 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-6mm	red	6 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-7mm	orange	7 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-8mm	yellow	8 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-10mm	blue	10 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-11mm	brown	11 mm	3" (76 mm)	7-5/16" (186 mm)	.20

## Cushion-Grip Hollow-Shaft Nut Drivers — 6" Shafts

### Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.



Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-3/16	black	3/16"	6" (152 mm)	9-3/4" (248 mm)	.25
646-1/4	red	1/4"	6" (152 mm)	9-3/4" (248 mm)	.25
646-5/16	yellow	5/16"	6" (152 mm)	9-3/4" (248 mm)	.25
646-11/32	green	11/32"	6" (152 mm)	9-3/4" (248 mm)	.25
646-3/8	blue	3/8"	6" (152 mm)	9-3/4" (248 mm)	.30

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-7/16	brown	7/16"	6" (152 mm)	10-5/16" (262 mm)	.35
646-1/2	red	1/2"	6" (152 mm)	10-5/16" (262 mm)	.35
646-9/16	orange	9/16"	6" (152 mm)	11-3/8" (289 mm)	.40
646-5/8	yellow	5/8"	6" (152 mm)	11-3/8" (289 mm)	.40

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.



## **Cushion-Grip Nut Drivers**

## Magnetic Tip Nut Drivers - Hollow Shafts\*

### Additional Feature:

 Exclusive hollow shaft\* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts.

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
610-1/4M	red	1/4"	3" (76 mm)	1-1/2" (89 mm)	.10
610-5/16M	yellow	5/16"	3" (76 mm)	1-1/2" (89 mm)	.10
610-3/8M	blue	3/8"	3" (76 mm)	1-1/2" (89 mm)	.10
630-3/16M*	black	3/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-1/4M	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	.20
630-5/16M	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-11/32M	green	11/32"	3" (76 mm)	6-3/4" (171 mm)	.20
630-3/8M	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	.20
630-7/16M	brown	7/16"	3" (76 mm)	7-5/16" (186 mm)	.25
630-1/2M	red	1/2"	3" (76 mm)	7-5/16" (186 mm)	.25
646-3/16M*	-3/16M* black 3/16"		6" (152 mm)	9-3/4" (248 mm)	.25



0
---

630-3/8M

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-1/4M	red	1/4"	6" (152 mm)	9-3/4" (248 mm)	.25
646-5/16M	yellow	5/16"	6" (152 mm)	9-3/4" (248 mm)	.25
646-11/32M	green	11/32"	6" (152 mm)	9-3/4" (248 mm)	.25
646-3/8M	blue	3/8"	6" (152 mm)	9-3/4" (248mm)	.30
646-7/16M	brown	7/16"	6" (152 mm)	10-5/16" (262 mm)	.35
646-1/2M	red	1/2"	6" (152 mm)	10-5/16" (262 mm)	.35
618-1/4M	red	1/4"	18" (457 mm)	21-3/4" (552 mm)	.50
618-5/16M	yellow	5/16"	18" (457 mm)	21-3/4" (552 mm)	.50

<sup>\*3/16&</sup>quot; magnetic nut driver does not have a hollow shaft.

## **Drive-A-Matic Cushion-Grip Nut Driver**



### 632

### Additional Features:

- Automatically fits 15 different nut and screw sizes.
- Hex head adjusts to the proper size as you turn it.
- Will drive or loosen hex nuts from 1/4" (6.4 mm) to 7/16" (11.1 mm), hex-head screws from No. 6 to 1/4" (6.4 mm), and socket-head cap screws from No. 8 to 5/16" (7.9 mm).

Cat. No.	Overall Length	Weight (lbs.)
632	7" (178 mm) when open, 6-3/4" (171 mm) when closed	.35

## **Coated Hollow-Shaft Nut Drivers**



### Additional Features:

- Entire shaft plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
640-3/16	black	3/16"	3" (76 mm)	6-3/4" (171 mm)	.25
640-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	.25
640-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	.25
640-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	.25
640-7/16	brown	7/16"	3" (76 mm)	7-5/16" (186 mm)	.30
640-1/2	red	1/2"	3" (76 mm)	7-5/16" (186 mm)	.25
640-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)	.40
640-5/8	yellow	5/8"	4" (102 mm)	9-3/8" (238 mm)	.40


 $\pmb{\triangle} \textbf{WARNING:}$  NOT insulated. Coating is intended for protection of circuits only.



All dimensions are in inches and (millimeters).

## Plastic-Handle, Hollow-Shaft Nut Driver Sets

## Features:



## 4-Piece Nut Driver Set — 3" Shafts

### Additional Feature:

Standard length works for most applications.

Cat. No.	Set Co	Set Contains					
70084						.60	
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length		
	S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)		
	S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)		
	S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	-	
	S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	-	



## 5-Piece Nut Driver Set — 3" Shafts

## Additional Features:

- Standard length works for most applications.
- Comes in a hang-up box.

Cat. No.	Set Co	Set Contains				
89969						.70
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
	S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
	S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	
	S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	
	S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	-
	S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	-



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.





## **Plastic-Handle, Hollow Shaft Nut Driver Sets**

(lbs.)

## 7-Piece Nut Driver Set — 3" Shafts

### Additional Feature:

• Set contains seven hollow-shaft nut drivers in the most popular hex sizes.

Cat. No.	Set Contains						
89004						1.10	
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length		
	S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)		
	S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	-	
	S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	-	
	S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	-	
	S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	-	
	S14	brown	7/16"	3" (76 mm)	7" (178 mm)	-	
	S16	red	1/2"	3" (76 mm)	7" (178 mm)		



## 7-Piece Nut Driver Set — 3" Shafts

### Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Convenient vinyl pouch hangs up or rolls up.

Cat. No.	Set Co	ntains				Weight (lbs.)
K7						1.15
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
	S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
	S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	•
	S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	•
	S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	
	S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	•
	S14	brown	7/16"	3" (76 mm)	7" (178 mm)	•
	S16	red	1/2"	3" (76 mm)	7" (178 mm)	



## 7-Piece Nut Driver Set With Metal Stand — 3" Shafts

## Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Metal holder stands freely or hangs on wall.

Cat. No.	NO. Set Contains					we
S700						1.60
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
	S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
	S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	
	S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	
	S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	
	S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	
	S14	brown	7/16"	3" (76 mm)	7" (178 mm)	
	S16	red	1/2"	3" (76 mm)	7" (178 mm)	



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

## **Plastic-Handle, Hollow Shaft Nut Driver Sets**

## 10-Piece Metric Nut Driver Set With Stand — 3" Shafts

### Additional Features:

- White enameled metal stand holds all ten 3"-shaft metric nut drivers.
- Identification label makes individual size selection easy.

Cat.No.	Set Con	tains				We
70200						1.8
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
	70204	black	4 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70245	black	4.5 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70205	black	5 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70255	black	5.5 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70206	black	6 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70207	black	7 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70208	black	8 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70209	black	9 mm	3" (76 mm)	6-5/8" (168 mm)	-
	70210	black	10 mm	3" (76 mm)	7" (178 mm)	-
	70211	black	11 mm	3" (76 mm)	7" (178 mm)	-
			_			-



70200

## 7-Piece Nut Driver Set — 6" Shafts

### Additional Feature:

• Contains seven 6"-shaft nut drivers that reach into deep recesses.

Cat. No.	Set Cor	ntains				Weigh
89904						1.15
	Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
	S66	black	3/16"	6" (152 mm)	9-5/8" (244 mm)	
	S86	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	_
	S106	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	-
	S116	green	11/32"	6" (152 mm)	9-5/8" (244 mm)	-
	S126	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	_
	S146	brown	7/16"	6" (152 mm)	10" (254 mm)	_
	S166	red	1/2"	6" (152 mm)	10" (254 mm)	_



## **Plastic-Handle, Hollow Shaft Nut Drivers**

## Stubby Nut Drivers — 1-1/2" Shafts

### Additional Feature:

Stubby nut drivers allow for work in close quarters.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
SS8	red	1/4"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15
SS10	amber	5/16"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15
SS12	blue	3/8"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15



SS10



**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

## **Plastic-Handle Nut Drivers**

## **Hollow-Shaft Nut Drivers** 3" & 4" Shafts



### Additional Features:

- Standard length works for most applications.
- Fits over long bolts and studs.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S5	amber	5/32"	3" (76 mm)	6-1/2" (165 mm)	.10
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	.10
S7	brown	7/32"	3" (76 mm)	6-5/8" (168 mm)	.10
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	.15
S9	orange	9/32"	3" (76 mm)	6-5/8" (168 mm)	.15
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	.15
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	.15
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	.15
S14	brown	7/16"	3" (76 mm)	7" (178 mm)	.20
S16	red	1/2"	3" (76 mm)	7" (178 mm)	.20
S18	red	9/16"	4" (102 mm)	8-1/2" (216 mm)	.30
S20	red	5/8"	4" (102 mm)	8-1/2" (216 mm)	.30

## Metric Nut Drivers — 3" Shafts



### Additional Features:

S10

70209

- Standard length works for most applications.
- Fits over long bolts and studs.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
70204	black	4 mm	3" (76 mm)	6-5/8" (168 mm)	.10
70245	black	4.5 mm	3" (76 mm)	6-5/8" (168 mm)	.10
70205	black	5 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70255	black	5.5 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70206	black	6 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70207	black	7 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70208	black	8 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70209	black	9 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70210	black	10 mm	3" (76 mm)	7" (178 mm)	.15
70211	black	11 mm	3" (76 mm)	7" (178 mm)	.20

## Nut Drivers — 6" Shafts



## Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S66	black	3/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S86	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	.15
S106	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S116	green	11/32"	6" (152 mm)	9-5/8" (244 mm)	.15
S126	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	.15
S146	brown	7/16"	6" (152 mm)	10" (254 mm)	.20

## Magnetic Nut Drivers — Solid Shafts



### Additional Feature:

Powerful nut-holding magnet built into solid shaft.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S8M	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	.15
S10M	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	.15
S86M	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	.15
S106M	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S126M	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	.15
S818M	red	1/4"	18" (457 mm)	21-5/8" (549 mm)	.25
S1018M	amber	5/16"	18" (457 mm)	21-5/8" (549 mm)	.25

## Super-Long Nut Drivers — 18" Shafts





- Heavy-duty, long-reach nut drivers.
- Ideal for reaching into walls and other hard-to-reach places where added length is necessary.
- Available in magnetic and non-magnetic tip.
- Overall Length: 21-5/8" (549 mm).

Cat. No.	Handle Color	Hex Size	Shaft Length	Туре	Weight (lbs.)
S818	red	1/4"	18" (457 mm)	standard	.25
S818M	red	1/4"	18" (457 mm)	magnetic	.25
S1018	amber	5/16"	18" (457 mm)	standard	.25
S1018M	amber	5/16"	18" (457 mm)	magnetic	.25

S1018

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

## **Tapping Tools and Awls**

## **Cushion-Grip Triple Taps and 6-in-1 Tap Tool**

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

Cat. No.	Tap Sizes	Overall Length	Weight (lbs.)
623-20	Triple Tap 10-24, 12-24, 1/4-20	7-3/4"	.25
623-24	Triple Tap 6-32, 8-32, 10-24	7-3/4"	.25
626	6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-3/4"	.25



626

Replacement Taps		
628-20	10-24, 12-24, 1/4-20	replacement for 623-20, 626
626-24	6-32, 8-32, 10-24	replacement for 623-24
626-32	6-32, 8-32, 10-32	replacement for 623-32, 626

## **6-in-1 Tapping Tool**



627-20

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.
- Two high-carbon steel taps are secured in reversible holder.

Cat. No.	Tap Sizes	Overall Length	Weight (lbs.)
627-20	6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-5/8" (194 mm)	0.35

Replace	ment Taps	
626-32	10-32, 8-32, 6-32	
628-20	10-24, 12-24, 1/4-20	

## **Triple Taps**



625-24

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

Cat. No.	Tap Sizes	Color Code	Overall Length	Weight (lbs.)		
625-24	6-32, 8-32, 10-24	blue	7-1/8" (181 mm)	0.20		
625-32	6-32, 8-32, 10-32	orange	7-1/8" (181 mm)	0.20		
Replacement Taps						
626-24	for Cat. No. 625-24					
626-32	for Cat. No. 625-32					

## **Cushion-Grip Scratch Awl**



- Professional, heavy-duty, hard-pointed awl.
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs.
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and for handle impact reinforcement.
- Internal flanges provide solid shank anchor.
- · Cushion-Grip handle allows for greater comfort.

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
650	3-1/2" (89 mm)	7-7/8" (200 mm)	.25

**AWARNING:** Do NOT hammer on tool.

## **Steel Scratch Awl**



66385

- One-piece forged-steel blade and bolstered shank.
- Heat treated for long life.
- Well-balanced for top efficiency during use.
- Black finish for rust resistance.

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
66385	3-1/2" (89 mm)	7" (178 mm)	.30

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.



## Scre & Ac



## **Spring Tools**

## **Cushion-Grip Spring Tool**



ST4

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, installing recessed can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.

Cat. No.	Shank Length	Overall Length	Weight (lbs.)
ST4	4" (102 mm)	7-3/4" (197mm)	.17
ST6	6" (152 mm)	9-3/4" (248 mm)	.19

## **Spring Tool**



ST49

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.

Cat. No.	Overall Length	Weight (lbs.)
ST49	7-1/2" (191 mm)	.10

## **Spring Tool Set**

## 2-Piece Recessed Can Light Tool Set

- Contains the two tools needed for finishing can light installations in record time.
- Long reach, spring tool (Cat. No. ST6) makes attaching difficult springs easy.
- Compact, stubby nut driver (Cat. No. 610-1/4) even fits in smaller cans to tighten hard to reach ceiling height adjustment screws.





65020

Cat. No.	Set Contains				Weight (lbs.)
65020					.36
	Cat. No.	Description	Shank Length	Overall Length	
	ST6	6" spring tool	6" (152 mm)	9-3/4" (248 mm)	
	610-1/4	1/4" stubby nut driver	1-1/2" (38 mm)	3-1/2" (89 mm)	<del></del>

All dimensions are in inches and (millimeters).





## **Power Tool Accessories**



## **Multi-Bit Power Drivers**

Klein Multi-Bit Power Drivers combine multiple screwdriver and nut driver functions in one power tool adapter. The solid body with 1/4" hex quick connect easily attaches to any power drill. Multi-Bit Power Drivers are designed and constructed to withstand the high RPMs and force of even the most aggressive impact driver. Allowing you to quickly change between functions – No more wasting time and money, searching for different accessories in your tool bag.

- Three screwdriver functions and three nut drivers in one power tool adaptor (Cat. No. 32606).
- Solid body with 1/4" hex quick connect for easy attachment to any power drill.
- Designed and constructed to withstand impact drills.



		Screwdriver		Nut Driver					
Cat. No.	Description	PH2	SQ2	SL 3/16"	1/4"	5/16"	3/8"	9/16"	Overall Length
32605	5-in-1 Multi-Bit Power Driver	•	0	•	0		0		4.25" (108 mm)
32606	6-in-1 Multi-Bit Power Driver	0	0	•	0	0		0	5.00" (127 mm)
Double-Ende	Double-Ended Replacement Bits								
32744	Replacement Bit for 32605 (3-pack)		0	•					
32745	Repalcement Bit for 32606 (3-pack)		0	•					



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.



.


## **Power Tool Accessories**



### **Power Drivers**

Klein Power Drivers are manufactured in the U.S.A. to ensure proper fit in every application. Each Power Driver is precision machined, heat treated and finished to the gold standards Klein Tools puts into every screwdriver blade. Proprietary processes create the longest life power driver bit in the industry. Tight fitting tips reduce wear and deliver the premium performance you, and the generations before you, expect from a Klein.

- Precision machined for better fit, more torque and less wear
- Custom heat treated for long life
- Available in a variety of tips







PH2-1-15 PH2-35-5

Cat. No.	Tip Size	Length	Pack Qty.
<b>Phillips</b>			
PH1-1-5	#1	1"	5
PH1-35-5	#1	3-1/2"	5
PH1-6-2	#1	6"	2
PH2-1-15	#2	1"	15
PH2-35-5	#2	3-1/2"	5
PH2-6-2	#2	6"	2
PH3-1-5	#3	1"	5
PH3-35-5	#3	3-1/2"	5
PH3-6-2	#3	6"	2
Slotted			
SL316-1-5	3/16"	1"	5
SL316-35-5	3/16"	3-1/2"	5
SL14-1-5	1/4"	1"	5
SL14-35-5	1/4"	3-1/2"	5

Cat. No.	Tip Size	Length	Pack Qty.				
O Square-Recess							
SQ1-1-5	#1	1"	5				
SQ1-35-5	#1	3-1/2"	5				
SQ1-6-2	#1	6"	2				
SQ2-1-15	#2	1"	15				
SQ2-35-5	#2	3-1/2"	5				
SQ2-6-2	#2	6"	2				
SQ3-1-5	#3	1"	5				
SQ3-35-5	#3	3-1/2"	5				
SQ3-6-2	#3	6"	2				

## **Power Conduit Reamer**

Reams conduit and installs fittings in a fraction of the time. Designed to fit into power drill chucks and quick release adapters, the power conduit reamer reduces time and wrist fatigue on projects with large quantities of conduit runs.



- Includes replaceable No. 2 square recess bit for installing conduit fittings.
- Includes precision engineered replaceable reaming blade.
- Designed to fit into power drill chucks and 1/4" quick release.

Cat. No.	Description
85091	conduit reamer drill head for 1/2", 3/4" and 1" conduit



Replacemen	Replacement Parts				
19353	conduit reamer replacement blade				
SQ2-1-15	#2 square recess replacement bits (15-pack)				

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.

## **Power Tool Accessories**



## **Power Nut Drivers**

Available in several sizes, these hollow shaft magnetic nut drivers are designed for long bolts, studs or threaded rod jobs. The magnetic head holds nuts and bolts to aid in hard to reach installations. The 5" and 10" models feature a wrench assist end, designed for high torque loosening found in many jobs.



Hollow magnetic\* shafts for nut running

- 5" and 10" models are sold individually.
- Power Nut Driver Set contains 1/4", 5/16" and 3/8" nut drivers (Cat. No. 32759).






PND71610

Cat. No.	Hex Sizes	Hollow Depth	Overall Length					
2" (127 mm) Out-of-Chuc	2" (127 mm) Out-of-Chuck							
32759	1/4", 5/16", 3/8"	1-7/8" (48 mm)	6.32" (80 mm)					
5" (127 mm) Out-of-Chuc	5" (127 mm) Out-of-Chuck							
PND7165	7/16"	3-13/16" (97 mm)	6.32" (161 mm)					
PND125	1/2"	3-23/32" (95 mm)	6.30" (160 mm)					
PND9165	9/16"	3-5/8" (92 mm)	6.33" (161 mm)					
10" (254 mm) Out-of-Chu	ck							
PND71610	7/16"	8-13/16" (223 mm)	11.32" (288 mm)					
PND1210	1/2"	8-23/32" (221 mm)	11.30" (287 mm)					
PND91610	9/16"	8-5/8" (219 mm)	11.33" (288 mm)					

\*Rare earth magnet is globally sourced.



**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use to pry or chisel.








## **Adjustable Wrenches**

## Features:



## **Adjustable Wrenches** — **High Capacity**

### Additional Features:

- Extra capacity allows use of a smaller size wrench to handle bigger jobs, especially in confined spaces.
- Forged heat-treated alloy steel for maximum strength and light weight.



Cat. No.	Handle Finish	Handle Color	Length	Capacity	Weight
507-6	high-polish chrome	-	6-3/8" (162 mm)	15/16" (24 mm)	0.29 lbs. (0.14 kg)
507-8	high-polish chrome	-	8-1/8" (206 mm)	1-1/8" (28 mm)	0.61 lbs. (0.28 kg)
507-10	high-polish chrome	-	10-1/8" (257 mm)	1-5/16" (33 mm)	0.98 lbs. (0.44 kg)
507-12	high-polish chrome	-	12-1/4" (311 mm)	1-1/2" (38 mm)	1.65 lbs. (0.75 kg)
D507-6	plastic dipped	transparent red	6-1/2" (165 mm)	15/16" (24 mm)	0.33 lbs. (0.15 kg)
D507-8	plastic dipped	transparent red	8-1/4" (209 mm)	1-1/8' (28 mm)	0.66 lbs. (0.30 kg)
D507-10	plastic dipped	transparent red	10-1/4" (260 mm)	1-5/16" (33 mm)	1.11 lbs. (0.50 kg)
D507-12	plastic dipped	transparent red	12-3/8" (314 mm)	1-1/2" (38 mm)	1.8 lbs. (0.81 kg)

## Adjustable Wrench — Extra-Wide Jaw

### Additional Features:

- Extra wide 1-1/2" jaw provides same capacity as a standard 12" adjustable wrench.
- Forged heat-treated alloy steel for maximum strength and light weight.





Cat. No.	Handle Finish	Handle Color	Length	Capacity	Weight
D509-8	plastic dipped	solid blue	8-1/2" (216 mm)	1-1/2" (38 mm)	0.77 lbs. (0.35 kg)

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: Do NOT push or hammer wrench.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



## **Adjustable Wrenches**

## Adjustable Wrenches — Standard Capacity

## Additional Features:

- Forged heat-treated alloy steel for maximum strength and light weight.
- High-polish chrome finish.




Cat. No.	Handle Color	Handle Finish	Length	Capacity	Weight (lbs.)
D506-4	transparent red	plastic-dipped	4-1/2" (114 mm)	1/2" (12 mm)	.13
506-15	-	high-polish chrome	15-7/8" (403 mm)	1-11/16" (42 mm)	2.92
500-18	-	high-polish chrome	18-1/4" (463 mm)	2-1/16" (52 mm)	4.67
500-24	-	high-polish chrome	24" (610 mm)	2-1/2" (63 mm)	7.76

## Adjustable-Head Construction Wrenches

- Eliminates the need to carry several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle.
- Industrial black finish for corrosion resistance.
- Includes lanyard hole for easy tool tethering.



Cat. No.	Max. Size Capacity	Length	Weight (lbs.)
3227	1-5/16" (33 mm)	11" (279 mm)	1.20
3239	1-1/2" (38 mm)	16" (406 mm)	2.36



**AWARNING:** Always wear approved eye protection.


**AWARNING:** Do NOT push or hammer wrench.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



## **Combination Wrenches**

### Features:



Weight (lbs.)



## Box ends have 15° angle offset to provide clearance over obstructions.

## 7-Piece Combination Wrench Set

Cat. No.	Set Contains	;			Weight (lbs.)
68400					1.23
	Cat. No.	Size	Length	Box End Point	
	68410	1/4"	5-1/8"	12	
	68411	5/16"	4-3/8"	12	
	68412	3/8"	6-1/8"	12	•
	68413	7/16"	6-3/8"	12	•
	68414	1/2"	7-1/8"	12	•
	68415	9/16"	7-1/2"	12	•
	68416	5/8"	8-1/8"	12	•
	Includes pouc	h with marked	d pockets for ea	ich wrench	•



68400

## 9-Piece Combination Wrench Set

Cat. No.	Set Contain	IS			Weig
68402					2.07
	Cat. No.	Size	Length	Box End Point	
	68410	1/4"	5-1/8"	12	
	68411	5/16"	4-3/8"	12	_
	68412	3/8"	6-1/8"	12	_
	68413	7/16"	6-3/8"	12	_
	68414	1/2"	7-1/8"	12	_
	68415	9/16"	7-1/2"	12	_
	68416	5/8"	8-1/8"	12	_
	68417	11/16"	9"	12	-
	68418	3/4"	9-1/8"	12	_
	Includes pou	ch with marl	ked pockets for	each wrench	-



68402

All dimensions are in inches.

**AWARNING:** Do NOT push or hammer wrench.

AWARNING: Do NOT extend handle length.

126

**AWARNING:** Always wear approved eye protection.

## **Combination Wrenches**

## **12-Piece Combination Wrench Set**

Cat. No.	Set Contains				Weigh (lbs.)
68404					4.13
	Cat. No.	Size	Length	Box End Point	
	68410	1/4"	5-1/8"	12	
	68411	5/16"	4-3/8"	12	
	68412	3/8"	6-1/8"	12	
	68413	7/16"	6-3/8"	12	
	68414	1/2"	7-1/8"	12	
	68415	9/16"	7-1/2"	12	
	68416	5/8"	8-1/8"	12	
	68417	11/16"	9"	12	
	68418	3/4"	9-1/8"	12	
	68419	13/16"	10-9/16"	12	
	68420	7/8"	11-1/2"	12	
	68421	15/16"	12-1/2"	12	
	Includes po	uch with r	narked pocke	ets for each wrench	



68404

## **14-Piece Combination Wrench Set**

Cat. No.	Set Con- tains				Weig (lbs.)
68406					9.75
	Cat. No.	Size	Length	Box End Point	
	68412	3/8"	6-1/8"	12	-
	68413	7/16"	6-3/8"	12	-
	68414	1/2"	7-1/8"	12	-
	68415	9/16"	7-1/2"	12	-
	68416	5/8"	8-1/8"	12	-
	68417	11/16"	9"	12	-
	68418	3/4"	9-1/8"	12	-
	68419	13/16"	10-9/16"	12	-
	68420	7/8"	11-1/2"	12	-
	68421	15/16"	12-1/2"	12	-
	68422	1"	13-1/2"	12	-
	68423	1-1/16"	14-5/8"	12	-
	68424	1-1/8"	15-9/16"	12	-
	68425	1-1/4"	16-7/8"	12	-
	Includes po	uch with m	narked pocke	ets for each wrench	-




68406

68417

1.88

## **Combination Wrenches**

Cat. No.	Size	Length	Box End Point	Weight (lbs.)
68410	1/4"	5-1/8"	12	.05
68411	5/16"	4-3/8"	12	.05
68412	3/8"	6-1/8"	12	.10
68413	7/16"	6-5/8"	12	.14
68414	1/2"	7-1/8"	12	.18
68415	9/16"	7-1/2"	12	.23
68416	5/8"	8-1/2"	12	.28
68417	11/16"	9"	12	.37
68418	3/4"	9-7/8"	12	.46




TOOLS 11/16

12

All dimensions are in inches.

**AWARNING:** Always wear approved eye protection.



16-3/4"

ANALY DESIGNATION

**AWARNING:** Do NOT extend handle length.

1-1/4"

68425





## **Combination Wrenches - Metric**

## 7-Piece Combination Wrench Set — Metric


Cat. No.	Set Conta	Weight (lbs			
68500					1.21
	Cat. No.	Size	Length	Box End Point	
	68507	7 mm	107 mm	12	
	68509	9 mm	119 mm	12	_
	68510	10 mm	135 mm	12	
	68511	11 mm	149 mm	12	
	68513	13 mm	166 mm	12	_
	68514	14 mm	178 mm	12	
	68515	15 mm	191 mm	12	_
	Includes po	uch with m	arked pockets f	or each wrench	



68500

## 11-Piece Combination Wrench Set — Metric

Cat. No.	Set Contain	Weight (lbs.)			
68502					2.35
	Cat. No.	Size	Length	Box End Point	
	68507	7 mm	107 mm	12	_
	68508	8 mm	110 mm	12	
	68509	9 mm	119 mm	12	_





68502

## **Combination Wrenches** — Metric

Cat. No.	Size	Length	Box End Poi	nt Weight (lbs.)
68507	7 mm	130 mm	12	.05
68508	8 mm	137 mm	12	.08
68509	9 mm	155 mm	12	.10
68510	10 mm	165 mm	12	.13
68511	11 mm	165 mm	12	.13
68512	12 mm	181 mm	12	.18
68513	13 mm	181 mm	12	.16
68514	14 mm	191 mm	12	.22
68515	15 mm	191 mm	12	.22
68517	17 mm	229 mm	12	.39
68519	19 mm	248 mm	12	.42



68512

All dimensions are in inches or millimeters.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT push or hammer wrench.

## **Open-End Wrenches**

### Features:



## **5-Piece Open-End Wrench Set**

Cat. No.	Set Contains				Weight (lbs.)
68450					1.08
	Cat. No.	Small Size	Large Size	Length	
	68460	1/4"	5/16"	4-3/4"	
	68461	3/8"	7/16"	6"	
	68462	1/2"	9/16"	7"	
	68463	9/16"	5/8"	7-1/2"	_
	68464	11/16"	3/4"	9"	_
	Includes pouch	with marked pocl	cets for each wrenc	ch	_



68450

## 7-Piece Open-End Wrench Set

Cat. No.	Set Contain	S			Weight (lbs.)
68452					2.46
	Cat. No.	Small Size	Large Size	Length	
	68460	1/4"	5/16"	4-3/4"	
	68461	3/8"	7/16"	6"	_
	68462	1/2"	9/16"	7"	
	68463	9/16"	5/8"	7-1/2"	
	68464	11/16"	3/4"	9"	_
	68465	13/16"	7/8"	10"	
	68466	15/16"	1"	11"	_
	Includes pour	ch with marked po	ckets for each w	rench	_



68452

## **Open-End Wrenches**

Cat. No.	Small Size	Large Size	Length	Weight (lbs.)
68460	1/4"	5/16"	4-3/4"	.04
68461	3/8"	7/16"	6"	.10
68462	1/2"	9/16"	7"	.17
68463	9/16"	5/8"	7-1/2"	.20
68464	11/16"	3/4"	9"	.36
68465	13/16"	7/8"	10"	.55
68466	15/16"	1"	11"	.80



68463

All dimensions are in inches or millimeters.

**AWARNING:** Do NOT push or hammer wrench.

 $\pmb{\hat{\textbf{A}}\textbf{WARNING:}}$  Do NOT extend handle length.

129

**AWARNING:** Always wear approved eye protection.

## **Socket Wrench Sets**

## 8-Piece 1/2-Inch Drive Deep-Socket Set



### Set consists of the following pieces:

- Eight 12-point deep sockets: 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", and 15/16".
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65514	complete 8-piece 1/2" drive, deep-socket set plus metal box	4.53

16-Piece 1/2-Inch Drive Socket



### Set consists of the following pieces:

- Thirteen 12-point sockets: 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 1-1/16", 1-1/8", and 1-1/4".
- One extension: 5" long.
- One flex handle: 17" long.
- One ratchet.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65512	complete 16-piece 1/2" drive set plus metal box	9.63

## 12-Piece 1/2-Inch Drive Socket Wrench Set



65510

### Set consists of the following pieces:

- Nine 12-point sockets: 7/16", 1/2",
   9/16", 5/8", 11/16", 3/4", 13/16", 7/8", and 15/16".
- One extension: 5" long.
- One spark plug socket: 5/8".
- One ratchet.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65510	complete 12-piece 1/2" drive set plus metal box	5.37

## 8-Piece 3/8-Inch Drive Deep-Socket Set



### Set consists of the following pieces:

- Eight 6-point deep sockets: 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4" and 13/16".
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65502	8-piece deep-socket 3/8" drive set plus metal box	2.66

## 13-Piece 3/8-Inch Drive Socket Set - Metric

### Set consists of the following pieces:

- Thirteen 6-point sockets: 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, and 19 mm.
- Handy, flip-lock tray.

Cat. No.	Description	Weight (lbs.)
65506	13 sockets plus flip-lock tray	1.33



## **Socket Wrench Sets**

## 9-Piece 3/8-Inch Drive "D" Socket **Wrench Set**



Special tool selection for telephone work on cable enclosures and pole hardware.



- Four 6-point deep sockets: 3/8", 7/16", 1/2", and 9/16".
- One 3/8"-drive reversible ratchet: 7-7/8" long.
- Two extensions: 3" and 5" long.
- One 9/16" combination wrench: 6-5/8" long.
- One 3/16" hex nut driver.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65503	complete 9-piece "D" wrench kit plus metal box	3.60

## 12-Piece 3/8-Inch Drive Socket **Wrench Set**



### Set consists of the following pieces:

- Four 6-point sockets: 3/8", 7/16", 1/2", and 9/16".
- Four 12-point sockets: 5/8", 11/16", 3/4", and 13/16".
- One spark plug socket: 5/8".
- Two extensions: 1-3/4" and 6" long.
- One ratchet.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65504	complete 12-piece 3/8" drive set plus metal box	3.62

## 20-Piece 3/8-Inch Drive Socket **Wrench Set**



### Set consists of the following pieces:

65503

- Four 6-point sockets: 3/8", 7/16", 1/2", and 9/16".
- Five 12-point sockets: 5/8", 11/16", 3/4", 13/16", and 7/8".
- Eight 6-point deep sockets: 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", and 13/16".
- Two extensions: 1-3/4" and 3" long.
- One ratchet.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65508	complete 20-piece 3/8" drive set plus metal box	5.40

## 13-Piece 1/4-Inch Drive Socket **Wrench Set**



### Set consists of the following pieces:

- Nine 6-point sockets: 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", and 1/2".
- One spinner handle.
- Two extensions: 2" and 6" long.
- One ratchet.
- Hinged metal box.

Cat. No.	Description	Weight (lbs.)
65500	complete 13-piece 1/4" drive set plus metal box	2.07





**AWARNING:** Always wear approved eye protection.



## **Socket Wrenches**

## 1/4-Inch Drive — Standard 6-Point Sockets

Cat. No.	Size	Weight (lbs.)
65600	3/16"	.02
65601	7/32"	.02
65602	1/4"	.02
65603	9/32"	.02
65604	5/16"	.02
65605	11/32"	.03
65606	3/8"	.04
65607	7/16"	.04
65608	1/2"	.05





## 1/4-Inch Drive — Deep 6-Point Sockets

Cat. No.	Size	Weight (lbs.)
65610	1/4"	.06
65611	9/32"	.06
65612	5/16"	.05
65613	11/32"	.07
65614	3/8"	.08
65615	7/16"	.09
65616	1/2"	.11



## 1/4-Inch Drivers and Extensions

Cat. No.	Description	Weight (lbs.)
65620	4-3/4" ratchet	.32
65621	spinner handle	.19
65622	2" extension	.05
65623	6" extension	.14
	(1)	D.





65623

65621

## 3/8-Inch Drive — Standard 12-Point Sockets

Cat. No.	Size	Weight (lbs.)
65704	5/8"	.08
65705	11/16"	.11
65706	3/4"	.12
65707	13/16"	.15
65708	7/8"	.19





65706

## 3/8-Inch Drive — Standard 6-Point Sockets

Cat. No.	Size	Weight (lbs.)
65700	3/8"	.05
65701	7/16"	.05
65702	1/2"	.06
65703	9/16"	.06





6570

## 3/8-Inch Drive — Metric 6-Point Sockets

Cat. No.	Size	Weight (lbs.)
65907	7 mm	.04
65908	8 mm	.04
65909	9 mm	.05
65910	10 mm	.05
65911	11 mm	.05
65912	12 mm	.06
65913	13 mm	.07
65914	14 mm	.08
65915	15 mm	.10
65916	16 mm	.09
65917	17 mm	.10
65918	18 mm	.11
65919	19 mm	.14



65919

## 3/8-Inch Drive — Deep 6-Point Sockets

Cat. No.	Size	Weight (lbs.)
65710	3/8"	.09
65711	7/16"	.10
65712	1/2"	.13
65713	9/16"	.15
65714	5/8"	.22
65715	11/16"	.27
65716	3/4"	.28
65717	13/16"	.34



65713

## **Socket Wrenches**

## 3/8-Inch Drivers and Extensions

Cat. No.	Description	Weight (lbs.)
65720	7-1/2" ratchet	.73
65721	1-1/2" extension	.09
65722	3" extension	.15
65723	6" extension	.30
65724	5/8" spark plug socket	.21



## 1/2-Inch Drive — **Standard 12-Point Sockets**

Cat. No.	Size	Weight (lbs.)
65800	7/16"	.12
65801	1/2"	.12
65802	9/16"	.12
65803	5/8"	.12
65804	11/16"	.16
65805	3/4"	.18
65806	13/16"	.19
65807	7/8"	.21
65808	15/16"	.27
65809	1"	.31
65810	1-1/16"	.36
65811	1-1/8"	.41
65812	1-1/4"	.55



65800

## 1/2-Inch Drive — **Deep 12-Point Sockets**



65829

## 1/2-Inch Drivers and Extensions

Cat. No.	Description	Weight (lbs.)
65820	10-1/2" ratchet	1.30
65821	5" extension	.45
65822	17" flex handle	1.83
65823	5/8" spark plug socket	.18



## **Ratcheting Box Wrenches**

## **Different size** For use in confined spaces and on long opening on each **Corrosion resistant. Durable** end. studs. chrome-plated finish. **Laminated construction for** greater strength. Reverse ratcheting action by simply

turning wrench over.

## LE IA EST\_\_\_\_\_\_1857

## **Ratcheting Box Wrenches**

## **5-Piece Ratcheting Box Wrench Set**

### Additional Features:

- Five ratcheting box wrenches packed in a vinyl 8-1/2"W x 10"H (216 mm x 254 mm) roll-up pouch with individual pockets.
- Wrenches flip over to reverse ratchet.

Cat. No.	Set Contai	ns			Weight (lbs.)
68221					1.45
	Cat. No.	Point	Size	Length	
	68200	12	1/4" x 5/16"	4-3/8" (112 mm)	
	68201	12	3/8" x 7/16"	5-1/2" (140 mm)	-
	68202	12	1/2" x 9/16"	6-7/8" (175 mm)	
	68203	12	5/8" x 11/16"	8-1/4" (216 mm)	-
	68204	12	5/8" x 3/4"	8-1/4" (216 mm)	-
					-



## 7-Piece Ratcheting Box Wrench Set

### Additional Feature:


• Set of the ratcheting box wrenches in vinyl roll-up pouch.

Cat. No.	Set Contains				Weight (lbs.)
68222					2.65
	Cat. No.	Point	Size	Length	
	68200	12	1/4" x 5/16"	4-3/8" (112 mm)	
	68201	12	3/8" x 7/16"	5-1/2" (140 mm)	
	68202	12	1/2" x 9/16"	6-7/8" (175 mm)	
	68203	12	5/8" x 11/16"	8-1/4" (216 mm)	
	68204	12	5/8" x 3/4"	8-1/4" (216 mm)	
	68205	12	11/16" x 3/4"	9-1/4" (235 mm)	
	68206	12	13/16" x 7/8"	9-1/4" (235 mm)	



68222

## **Ratcheting Box Wrenches**





6820

Cat. No.	Point	Size	Length	Weight (lbs.)
68204	12	5/8" x 3/4"	8-1/4" (216 mm)	.42
68205	12	11/16" x 3/4"	9-1/4" (235 mm)	.52
68206	12	13/16" x 7/8"	9-1/4" (235 mm)	.69

## **3-Piece Fully Reversible Ratcheting Offset Box Wrench Set**

- Set of three offset and fully reversible ratcheting box wrenches.
- Different size single-hex openings on each end.
- Includes heavy-duty vinyl pouch.

Cat. No.	Set Contai	Set Contains			Weight (lbs.)
68244					.61
	Cat. No.	Point	Size	Length	
	68234	6	1/4" x 5/16"	4-3/8" (112 mm)	•
	68236	6	3/8" x 7/16"	5-1/2" (140 mm)	
	68238	6	1/2" x 9/16"	6-3/4" (171 mm)	-



68244

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: Do NOT push or hammer wrench.

**AWARNING:** Do NOT use on or near live electrical circuits.

**AWARNING:** Do NOT extend handle length.

## **Ratcheting Offset Box Wrenches**

## 5-Piece Fully Reversible Ratcheting Offset Box Wrench Set

- Set of the offset reversible ratchet box wrenches in vinyl roll-up pouch.
- Two grommet holes for hanging.

Cat. No.	Set Contai	ns			Weight (lbs.)
68245					1.57
	Cat. No.	Point	Size	Length	
	68234	6	1/4" x 5/16"	4-3/8" (112 mm)	
	68236	6	3/8" x 7/16"	5-1/2" (140 mm)	
	68238	6	1/2" x 9/16"	6-3/4" (171 mm)	
	68240	12	5/8" x 11/16"	8-1/8" (206 mm)	•
	68242	12	3/4" x 7/8"	9-1/8" (232 mm)	



68245

## **Fully Reversible Ratcheting Offset Box Wrenches**

- Both ends are offset 25° for more convenient use in confined spaces.
- Quick-flip reversing lever for instant ratchet reversal.
- · Laminated construction for greater strength.
- Chrome-plated for rust resistance.
- Different size openings at each end.

Cat. No.	Point	Size	Length	Weight (lbs.)
68234	6	1/4" x 5/16"	4-3/8" (112 mm)	.13
68236	6	3/8" x 7/16"	5-1/2" (140 mm)	.18
68238	6	1/2" x 9/16"	6-3/4" (171 mm)	.30
68240	12	5/8" x 11/16"	8-1/8" (206 mm)	.46
68242	12	3/4" x 7/8"	9-1/8" (232 mm)	.50



68236

## **Ratcheting Refrigeration Wrenches**

- Fully reversible ratchet wrenches designed for refrigeration-packing gland nuts and valve stem sockets.
- Wrenches are compact in size, with clearly marked sockets for four nut sizes.
- Also designed for beam-clamp installation.
- Quick-flip reversing lever permits instant ratchet reversal.
- Wrenches are ruggedly built and have polished chrome finish with smooth edges for comfort.



68310

Cat. No.	Socket Sizes	Length	Weight (lbs.)
68309	3/16" and 1/4" sq. x 1/2" and 9/16" hex	6-13/16" (173 mm)	.43
68310	3/16" and 5/16" sq. x 1/4" and 3/8" sq.	5-1/2" (140 mm)	.20
68310-24	24 pack of Cat. No. 68310	5-1/2" (140 mm)	4.70

## **Specialty Wrenches**

## **Can Wrench**

- Two tools in one; saves space in your pouch.
- One end opens telephone box fasteners, the other end tightens nuts on binding-post terminals.
- The 7/16" socket has a black finish and the 3/8" socket has a silver finish.
- Sockets are 1-1/4" (32 mm) deep to fit over long binding postsand are thin-walled for easy access into tight areas.
- Socket ends are color-coded for quick identification of socket sizes.
- Hex-socket design enables using a wrench to obtain extra torque.
- High-impact, break-resistant handle for long and dependable service.
- Sockets are heat-treated, alloy steel.



68005

Cat. No.	Description	Length	Handle Dia.	Weight (lbs.)
68005	3/8" and 7/16" hex nut	7" (178 mm)	1" (25 mm)	.35

AWARNING: NOT insulated. Will NOT protect against electrical shock.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT push or hammer wrench.

**AWARNING:** Do NOT use on or near live electrical circuits.



## **Specialty Wrenches**

## **Bell System Type**

 Similar to standard lineman's wrench, but with end openings sized to NEMA hardware specifications.





3146

Cat. No.	Description	Length	Weight (lbs.)
3146B	Large end has 1-1/16" and 1-3/16" openings. Small end has 11/16" and 7/8" openings.	13" (330 mm)	1.76

## **Lineman's Wrenches**

- · Forged from special bar steel and heat-treated for long life.
- Each end has two different size openings.
- Hole is provided at larger end for turning-in standard pole steps.
- Wrench is suited for use on heavy three-bolt guy clamps on which clearance is limited.

<ul><li>Dark blue</li></ul>	Dark blue painted finish (small end is painted silver on Cat. No. 3146A).					
Cat. No.	Description	Length	Weight (lbs.)			
3146	For 5/8" hardware. Large end has 29/32" and 1-3/32" openings. Small end has 5/8" and 13/16" openings.	13" (330 mm)	1.85			
31464	For 3/4" hardware, Large end has 1-1/16" and 1-5/16" openings, Small end has 5/8" and 7/8" openings	13" (330 mm)	1 70			

## 3-in-1 Impact Socket – Distribution | Transmission

- NRHD Distribution socket features three square socket sizes: 3/4", 1", and 1-1/8".
- NRHD2 Transmission socket features three square socket sizes: 1-1/8". 1-5/16". and 1-1/2".
- 7/16" hex guick-change adapter included.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- · Long hollow shaft allows use on long threaded bolts.

Cat. No.	Description	Length	Weight (lbs.)
NRHD	3-in1 Impact Socket	7-3/4" (197 mm)	2.0
NRHD2	11" (279.4 mm)	3.25 lbs. (1.47 kg)	3.25 <b>NEW!</b>



## **Impact Socket Adapters**

- 7/16" hex guick-change adapter.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- Do not exceed 200 ft. lbs of torque.

Cat. No.	Description	Length	Weight (oz.)
NRHDA	Distribution Socket Adapter	7/16"	5.8
NHRDA2	Transmission Socket Adapter	7/16"	10.9 <b>NEW!</b>



## **Lineman's Ratcheting Wrenches**

- Bolt-through design allows bolts to pass through the socket.
- 3/4" and 1" x 1-1/8" combination square socket for most common utility hardware.
- Bright yellow socket for easy visibility.
- Works on most common utility pole hardware, such as lag bolts, "C" clamps and suspension bolts.
- KT155T and KT155HD also offer two popular wrench sizes: 9/16" and 3/4".
- Heavy duty design (KT155HD).

Cat. No.	Description	Length	Weight (lbs.)
KT151T	Ratcheting Lineman's Wrench	13" (330 mm)	2.12
KT155HD	Ratcheting Lineman's Wrench – Heavy Duty	12" (305 mm)	2.10
KT155T	5-in-1 Lineman's Wrench	9-3/8" (238 mm)	1.42



KT155HD



KT155T

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

AWARNING: Do NOT push or hammer wrench.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock



## **Specialty Wrenches**

## Lineman's 4-in-1 Box Wrenches

- · Chrome plated finish resists corrosion.
- "See-through" insulating handle confirms metal ends are not connected (Cat. No. KT223X4-INS).
- 1/2", 9/16", 5/8" and 3/4" sizes in one tool; 12-point sockets.
- Reverse ratcheting action by reversing switches on each end of the wrench.
- Textured grooves in handle prevent slipping.
- Solid, one piece design (Cat. No. KT223X4).



Cat. No.	Description	Socket Size	Length	Weight (lbs.)
KT223X4-INS	Insulating Lineman's Box Wrench	1/2", 9/16", 5/8" & 3/4"	9" (229 mm)	.70
KT223X4	Lineman's Ratcheting Box Wrench	1/2", 9/16", 5/8" & 3/4"	9" (229 mm)	.70

KT223X4

## **Construction Wrenches**

## Adjustable-Head Construction Wrenches

- Eliminates the need for carrying several fixed-size wrenches.
- Forged from select alloy steel with continuous taper handle for aligning bolt and/or rivet holes.
- Industrial black finish for corrosion resistance.
- Includes lanyard hole for easy tool tethering.



Cat. No.	Max. Size Capacity	Length	Weight (lbs.)
3239	1-1/2" (38 mm)	16" (406 mm)	2.36
3227	1-5/16" (33 mm)	11" (279 mm)	1.20

## 1/2"-Drive Ratcheting Construction Wrench


- Accepts 1/2" square-drive hex socket.
- Reversible ratchet.
- Eliminates the need for carrying several fixed-size wrenches.
- Forged from select alloy steel with continuous taper handle for aligning bolt and/or rivet holes.
- Industrial black finish for corrosion resistance.

The state of the s	
	3238

Cat. No.	Overall Length	Weight (lbs.)
3238	15" (381 mm)	2.10

## **Erection Wrenches**

- Forged from select alloy steel to withstand high-leverage and heavy loads.
- Extra-heavy-duty head area gives maximum strength and durability.
- Continuous taper of handle makes lining-up bolt holes easy and works on a range of bolt-hole sizes without binding.
- Extra-large hub area works on larger diameter holes better than other wrenches
- Catalog number, bolt size and nominal opening size are stamped on every wrench for easy identification.
- American Bridge design.



Vat. No.	Nut Type	Size	Nom. Opening	Head Width	eter	Length	(lbs.)
3210	U.S. heavy	1/2"	7/8"	2-1/4"	7/8" to 3/16"	14-3/4"	1.36
3211	U.S. heavy	5/8"	1-1/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3212	U.S. heavy	3/4"	1-1/4"	2-1/2"	1" to 1/4"	16-5/8"	1.98
3213	U.S. heavy	7/8"	1-7/16"	3"	1-1/8" to 9/32"	17-3/8"	2.72
3214	U.S. heavy	1"	1-5/8"	3-5/8"	1-1/8" to 1/4"	18"	3.36
3219	U.S. regular	1/2"	3/4"	2-1/4"	7/8" to 8/16"	14-3/4"	1.36
3220	U.S. regular	1/2"	13/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.35

Cat. No.	Nut Type	Bolt Size	Nom. Opening	Head Width	Taper Diam- eter	Overall Length	Weight (lbs.)
3221	U.S. regular	5/8"	1"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3222	U.S. regular	3/4"	1-1/8"	2-1/2"	1" to 1/4"	16-5/8"	2.00
3223	U.S. regular	7/8"	1-5/16"	3"	1-1/8" to 9/32"	17-3/8"	2.87
3224	U.S. regular	1"	1-1/2"	3-5/8"	1-1/8" to 1/4"	18"	3.37
3231	utility	5/8"	15/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3232	utility	3/4"	1-1/16"	2-1/2"	1" to 1/4"	16-5/8"	2.00

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT push or hammer wrench.



## **Strap Wrenches**

## **Grip-It® Strap Wrenches**

- Completely adjustable strap wrench.
- Works in the tightest quarters.
- Urethane-covered, high-strength belting attached to lightweight, I-beam handle.
- Patented, cam-action design permits uniform, high-torque application.
- Under normal conditions, will not scratch, damage or deform polished pipe and fittings, plastic pipe and fittings, oil and water filters, glass pipe, PVC conduit, or polished shafts.
- Also works on alternator belts, flywheels, and propeller assemblies.



Cat. No.	Handle Length	Diameter Capacity, O.D.	Weight (lbs.)
S6H	6" (152 mm)	1-1/2" - 5" (38 mm - 127 mm)	.20
S12H	12" (305 mm)	1-1/2" - 5" (38 mm - 127 mm)	.80
S18H	18" (457 mm)	1-1/8" - 8" (28 mm - 228 mm)	2.95

## **Torque Wrenches**

## Micro-Adjustable Torque-Sensing Wrenches with Square-Drive Ratchet Head

- Automatically limits desired torque.
- "Torque by feel." Pull and click-it's torqued to micrometer accuracy.
- Ratchet head allows speedy torquing and operation in confined working areas.
- Torques to the right.



Cat. No.	Drive Size	Range	Length	Weight (lbs.)
57000	3/8"	15 – 75 ft-lb (20.4 – 101.7 Nm)	14-1/8" (359 mm)	2.00
57005	3/8"	30 - 150 in-lb (3.4 - 16.9 Nm)	10-5/8" (270 mm)	1.20
57010	1/2"	50 - 250 ft-lb (67.8 - 339.0 Nm)	24-1/4" (616 mm)	3.65

## **Master Electrician's Torque Tool Kit**

- Two micrometer-adjustable torque wrenches.
- Nine hex-wrench bits.
- Two 7/16" hex-wrench extensions.
- One 7/16" female hex-wrench adaptor (Coupler).
- One hex-to-square adapter for wrenches and one adaptor for screwdrivers.
- One adjustable torque screwdriver.
- Seven screwdriver bits; five slotted, two Phillips.
- Hinged metal box.
- Additional torque screwdrivers available in screwdriver section.

Cat. No.	Description	Weight (lbs.)
57060	master electrician's torque tool kit	9.55





**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT push or hammer wrench.





## **Journeyman™ T-Handle Hex-Keys**



## T-Handle Ball-End Hex-Key Set with Stand - Inch

### Additional features

- Metal stand for convenient hanging, storage on bench or wall.
- Short blade-through handle provides maximum tool versatility.

### 6" Length

Cat. No.	Set Contains			Weight (lbs.)
JTH610EB				3.0
	Cat. No.	Hex Size	Blade Length	
	JTH6E06BE	3/32"	6" (152 mm)	
	JTH6E07BE	7/64"	6" (152 mm)	
	JTH6E08BE	1/8"	6" (152 mm)	
	JTH6E09BE	9/64"	6" (152 mm)	
	JTH6E10BE	5/32"	6" (152 mm)	_
	JTH6E11BE	3/16"	6" (152 mm)	
	JTH6E12BE	7/32"	6" (152 mm)	
	JTH6E13BE	1/4"	6" (152 mm)	
	JTH6E14BE	5/16"	6" (152 mm)	
	JTH6E15BE	3/8"	6" (152 mm)	

## T-Handle Ball-End Hex-Keys — Inch

### Additional features

- Short blade-through handle provides maximum tool versatility.
- Black oxide tips for precision fit.

## 6" Length

Cat. No.	Hex Size	Blade Length	Weight (lbs.)
JTH6E06BE	3/32"	6" (152 mm)	.04
JTH6E07BE	7/64"	6" (152 mm)	.05
JTH6E08BE	1/8"	6" (152 mm)	.06
JTH6E09BE	9/64"	6" (152 mm)	.07
JTH6E10BE	5/32"	6" (152 mm)	.12
JTH6E11BE	3/16"	6" (152 mm)	.14





Hex Size	Blade Length	Weight (lbs.)
7/32"	6" (152 mm)	.17
1/4"	6" (152 mm)	.27
5/16"	6" (152 mm)	.35
3/8"	6" (152 mm)	.45
1/2"	6" (152 mm)	.70
	7/32" 1/4" 5/16" 3/8"	7/32" 6" (152 mm) 1/4" 6" (152 mm) 5/16" 6" (152 mm) 3/8" 6" (152 mm)

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

140

JTH610E

## T-Handle Hex-Key Sets with Stand - Inch

### Additional features

- Metal stand for convenient mounting on bench or wall.
- Short blade-through handle provides maximum tool versatility.

Set Contains			Weight (II
			2.7
Cat. No.	Hex Size	Blade Length	
JTH4E06	3/32"	4" (102 mm)	
JTH4E07	7/64"	4" (102 mm)	
JTH4E08	1/8"	4" (102 mm)	
JTH4E09	9/64"	4" (102 mm)	
JTH4E10	5/32"	4" (102 mm)	
JTH4E11	3/16"	4" (102 mm)	
JTH4E12	7/32"	4" (102 mm)	
JTH4E13	1/4"	4" (102 mm)	
JTH4E14	5/16"	4" (102 mm)	
JTH4E15	3/8"	4" (102 mm)	
	Cat. No.       JTH4E06       JTH4E07       JTH4E08       JTH4E09       JTH4E10       JTH4E11       JTH4E12       JTH4E13       JTH4E14	Cat. No.         Hex Size           JTH4E06         3/32"           JTH4E07         7/64"           JTH4E08         1/8"           JTH4E09         9/64"           JTH4E10         5/32"           JTH4E11         3/16"           JTH4E12         7/32"           JTH4E13         1/4"           JTH4E14         5/16"	Cat. No.         Hex Size         Blade Length           JTH4E06         3/32°         4° (102 mm)           JTH4E07         7/64°         4° (102 mm)           JTH4E08         1/8°         4° (102 mm)           JTH4E09         9/64"         4° (102 mm)           JTH4E10         5/32°         4° (102 mm)           JTH4E11         3/16°         4° (102 mm)           JTH4E12         7/32°         4° (102 mm)           JTH4E13         1/4°         4° (102 mm)           JTH4E14         5/16°         4° (102 mm)



Cat. No.	Set Contains			Weight (lbs.
JTH610E				2.7
	Cat. No.	Hex Size	Blade Length	
	JTH6E06	3/32"	6" (152 mm)	
	JTH6E07	7/64"	6" (152 mm)	
	JTH6E08	1/8"	6" (152 mm)	
	JTH6E09	9/64"	6" (152 mm)	
	JTH6E10	5/32"	6" (152 mm)	
	JTH6E11	3/16"	6" (152 mm)	
	JTH6E12	7/32"	6" (152 mm)	
	JTH6E13	1/4"	6" (152 mm)	
	JTH6E14	5/16"	6" (152 mm)	
	JTH6E15	3/8"	6" (152 mm)	


## 9" Length

Cat. No.	Set Contains			Weight (lbs.)
JTH910E				3.56
	Cat. No.	Hex Size	Blade Length	
	JTH9E06	3/32"	9" (229 mm)	_
	JTH9E07	7/64"	9" (229 mm)	
	JTH9E08	1/8"	9" (229 mm)	
	JTH9E09	9/64"	9" (229 mm)	
	JTH9E10	5/32"	9" (229 mm)	
	JTH9E11	3/16"	9" (229 mm)	
	JTH9E12	7/32"	9" (229 mm)	
	JTH9E13	1/4"	9" (229 mm)	
	JTH9E14	5/16"	9" (229 mm)	
	JTH9E15	3/8"	9" (229 mm)	

## T-Handle Hex-Keys - Inch

### Additional features

- Short blade-through handle provides maximum tool versatility.
- Black oxide tips for precision fit.



4" Length 6" Length

Cat. No.	Hex Size	Blade Length	Weight (oz.)	Cat. No.	Hex Size	Blade Length	Weight (lbs.)	Cat. No.	Hex Size	Blade Length	Weight (lbs.)
JTH4E06	3/32"	4" (102 mm)	.04	JTH6E06	3/32"	6" (152 mm)	.04	JTH9E06	3/32"	9" (229 mm)	.05
JTH4E07	7/64"	4" (102 mm)	.05	JTH6E07	7/64"	6" (152 mm)	.05	JTH9E07	7/64"	9" (229 mm)	.05
JTH4E08	1/8"	4" (102 mm)	.05	JTH6E08	1/8"	6" (152 mm)	.05	JTH9E08	1/8"	9" (229 mm)	.06
JTH4E09	9/64"	4" (102 mm)	.06	JTH6E09	9/64"	6" (152 mm)	.06	JTH9E09	9/64"	9" (229 mm)	.07
JTH4E10	5/32"	4" (102 mm)	.11	JTH6E10	5/32"	6" (152 mm)	.11	JTH9E10	5/32"	9" (229 mm)	.11
JTH4E11	3/16"	4" (102 mm)	.13	JTH6E11	3/16"	6" (152 mm)	.13	JTH9E11	3/16"	9" (229 mm)	.14
JTH4E12	7/32"	4" (102 mm)	.15	JTH6E12	7/32"	6" (152 mm)	.15	JTH9E12	7/32"	9" (229 mm)	.17
JTH4E13	1/4"	4" (102 mm)	.24	JTH6E13	1/4"	6" (152 mm)	.24	JTH9E13	1/4"	9" (229 mm)	.27
JTH4E14	5/16"	4" (102 mm)	.30	JTH6E14	5/16"	6" (152 mm)	.30	JTH9E14	5/16"	9" (229 mm)	.35
JTH4E15	3/8"	4" (102 mm)	.38	JTH6E15	3/8"	6" (152 mm)	.38	JTH9E15	3/8"	9" (229 mm)	.45
JTH4E17	1/2"	4" (102 mm)	.59	JTH6E17	1/2"	6" (152 mm)	.59	JTH9E17	1/2"	9" (229 mm)	.70

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Always wear approved eye protection.

## T-Handle Ball-End Hex-Key Set with Stand - Metric

### Additional features

- Metal stand for convenient mounting on bench or wall.
- Short blade-through handle provides maximum tool versatility.

### 6" Length

Set Contains			Weight (lbs.)
			2.7
Cat. No.	Hex Size	Blade Length	
JTH6M2BE	2 mm	6" (152 mm)	
JTH6M25BE	2.5 mm	6" (152 mm)	_
JTH6M3BE	3 mm	6" (152 mm)	_
JTH6M4BE	4 mm	6" (152 mm)	
JTH6M5BE	5 mm	6" (152 mm)	
JTH6M6BE	6 mm	6" (152 mm)	
JTH6M8BE	8 mm	6" (152 mm)	
JTH6M10BE	10 mm	6" (152 mm)	
	Cat. No.       JTH6M2BE       JTH6M25BE       JTH6M3BE       JTH6M4BE       JTH6M5BE       JTH6M6BE       JTH6M8BE	JTH6M2BE         2 mm           JTH6M25BE         2.5 mm           JTH6M3BE         3 mm           JTH6M4BE         4 mm           JTH6M5BE         5 mm           JTH6M6BE         6 mm           JTH6M8BE         8 mm	Cat. No.         Hex Size         Blade Length           JTH6M2BE         2 mm         6° (152 mm)           JTH6M25BE         2.5 mm         6° (152 mm)           JTH6M3BE         3 mm         6° (152 mm)           JTH6M4BE         4 mm         6° (152 mm)           JTH6M5BE         5 mm         6° (152 mm)           JTH6M6BE         6 mm         6° (152 mm)           JTH6M8BE         8 mm         6° (152 mm)



## T-Handle Ball-End Hex-Keys — Metric

### Additional features

- Short blade-through handle provides maximum tool versatility.
- Black oxide tips for precision fit.

Cat. No.	Hex Size	Blade Length	Weight (lbs.)
JTH6M2BE	2 mm	6" (152 mm)	.04
JTH6M25BE	2.5 mm	6" (152 mm)	.05
JTH6M3BE	3 mm	6" (152 mm)	.06
JTH6M4BE	4 mm	6" (152 mm)	.07
JTH6M5BE	5 mm	6" (152 mm)	.15
JTH6M6BE	6 mm	6" (152 mm)	.19
JTH6M8BE	8 mm	6" (152 mm)	.35
JTH6M10BE	10 mm	6" (152 mm)	.48



## T-Handle Hex-Key Sets with Stand - Metric

### Additional features

- Metal stand for convenient mounting on bench or wall.
- Short blade-through handle provides maximum tool versatility.

6" (152 mm)

6" (152 mm)

6" (152 mm)

6" (152 mm)

### 6" Length

Vat. No.	Set Contains			weight (lbs.)
JTH68M				1.84
	Cat. No.	Hex Size	Blade Length	
	JTH6M2	2 mm	6" (152 mm)	
	JTH6M25	2.5 mm	6" (152 mm)	
	JTH6M3	3 mm	6" (152 mm)	

4 mm

5 mm

6 mm

8 mm JTH6M10 10 mm 6" (152 mm)

JTH6M4

JTH6M6

JTH6M8

### 9" Length

Cat No.

JTH98M				2
	Cat. No.	Hex Size	Blade Length	
	JTH9M2	2 mm	9" (229 mm)	
	JTH9M25	2.5 mm	9" (229 mm)	
	JTH9M3	3 mm	9" (229 mm)	
	JTH9M4	4 mm	9" (229 mm)	
	JTH9M5	5 mm	9" (229 mm)	
	JTH9M6	6 mm	9" (229 mm)	
	JTH6M8	8 mm	9" (229 mm)	
	JTH9M10	10 mm	9" (229 mm)	



**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

# Hex-Key Wrench

## T-Handle Hex-Keys — Metric

### Additional features

- Short blade-through handle provides maximum tool versatility.
- Black oxide tips for precision fit.



### 6" Length

Cat. No.	Hex Size	Blade Length	Weight (lbs.)
JTH6M2	2 mm	6" (152 mm)	.04
JTH6M25	2.5 mm	6" (152 mm)	.05
JTH6M3	3 mm	6" (152 mm)	.06
JTH6M4	4 mm	6" (152 mm)	.07
JTH6M5	5 mm	6" (152 mm)	.15
JTH6M6	6 mm	6" (152 mm)	.17
JTH6M8	8 mm	6" (152 mm)	.35
JTH6M10	10 mm	6" (152 mm)	.48

## 9" Length

Cat. No.	Hex Size	Blade Length	Weight (oz.)
JTH9M2	2 mm	9" (229 mm)	.05
JTH9M25	2.5 mm	9" (229 mm)	.06
JTH9M3	3 mm	9" (229 mm)	.07
JTH6M4	4 mm	9" (229 mm)	.10
JTH9M5	5 mm	9" (229 mm)	.18
JTH9M6	6 mm	9" (229 mm)	.23
JTH9M8	8 mm	9" (229 mm)	.42
JTH9M10	10 mm	9" (229 mm)	.48

## T-Handle Hex-Key Set with Stand — TORX®

### Additional features

- Metal stand for convenient mounting on bench or wall.
- Short blade-through handle provides maximum tool versatility.

Cat. No.	Set Contains	3		Weight (lbs.)
JTH67T				1.32
	Cat. No.	Hex Size	Blade Length	
	JTH6T10	T10	6" (152 mm)	-
	JTH6T15	T15	6" (152 mm)	•
	JTH6T20	T20	6" (152 mm)	
	JTH6T25	T25	6" (152 mm)	
	JTH6T27	T27	6" (152 mm)	
	JTH6T30	T30	6" (152 mm)	
	JTH6T40	T40	6" (152 mm)	-



## T-Handle Hex-Keys — TORX®

### Additional features

- Short blade-through handle provides maximum tool versatility.
- Black oxide tips for precision fit.

Cat. No.	Hex Size	Blade Length	Weight (lbs.)
JTH6T10	T10	6" (152 mm)	.05
JTH6T15	T15	6" (152 mm)	.06
JTH6T20	T20	6" (152 mm)	.07
JTH6T25	T25	6" (152 mm)	.13
JTH6T27	T27	6" (152 mm)	.16
JTH6T30	T30	6" (152 mm)	.18
JTH6T40	T40	6" (152 mm)	.29



TORX® is a trademark of Acument Intellectual Properties, LLC.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.



# **Folding Hex-Key Sets**

#### **Hex-Key Sets**

- Two key positions (straight-out or right angle) for extra leverage.
- Hex ends are square-cut for a secure full-depth fit and maximum contact with the hex socket to prevent slippage and stripping of the socket.
- Handy sets fit in your pocket or tool box easily and help eliminate the lost key problem.



Description	Handle Length	Key Lengths	Weight (lbs.)
ets – Inch	·		
nine-key inch set: 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	4-1/4" (108 mm)	1-3/4" - 3-1/2" (44 mm - 89 mm)	.50
eight-key inch set: .050", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32"	3-1/16" (78 mm)	1-1/2" - 2-3/8" (38 mm - 60 mm)	.20
eight-key inch set: 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	5-1/4" (133 mm)	3-3/8" - 4-5/8" (86 mm - 117 mm)	.65
five-key inch set: 3/16", 7/32", 1/4", 5/16", 3/8"	5-1/4" (133 mm)	3" - 4-5/8" (76 mm - 117 mm)	.85
ets – Metric			
seven-key metric set: 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm, 6 mm	92 mm (3-5/8")	41 mm – 76 mm (1-5/8" – 3")	.35
five-key metric set: 4 mm, 5 mm, 6 mm, 8 mm, 10 mm	133 mm (5-1/4")	82 mm - 117 mm (3-1/4" - 4-5/8")	.85
	ets — Inch nine-key inch set: 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" eight-key inch set: .050", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" eight-key inch set: 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" five-key inch set: 3/16", 7/32", 1/4", 5/16", 3/8" ets — Metric seven-key metric set: 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm, 6 mm	nine-key inch set: 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" 4-1/4" (108 mm) eight-key inch set: .050", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" 3-1/16" (78 mm) eight-key inch set: 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" 5-1/4" (133 mm) five-key inch set: 3/16", 7/32", 1/4", 5/16", 3/8" 5-1/4" (133 mm) ets – Metric seven-key metric set: 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm, 6 mm 92 mm (3-5/8")	nine-key inch set: 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"

### **Grip-It® Hex-Key Sets**

- Blades rotate independently up to 270°.
- Precision fit so hex tool end reduces stripping problems. Keys are industrial strength, impact-resistant and tested for performance to below freezing.
- Glass-reinforced nylon handle.
- Hex ends are square-cut for a secure full-depth fit and maximum contact with the hex socket to prevent slippage and stripping of the socket (Cat. Nos. 70570, 70573, 70574, and 70575).
- Ball design allows for a thicker neck diameter increasing torque capacity, while maintaining operational angles to 25% (Cat. Nos. 70571 and 70572).



Cat. No.	Description	Sizes	Color	Weight (lbs.)
70570	Grip-It® hex sets – 5 inch sizes	3/16", 7/32", 1/4", 5/16", 3/8"	yellow	.58
70571	Grip-It® ball hex set – 5 inch sizes	3/16", 7/32", 1/4", 5/16", 3/8"	yellow	.58
70572	Grip-It® ball hex set – 5 metric sizes	5 mm, 6 mm, 7 mm, 8 mm, 10 mm	red	.58
70573	Grip-It <sup>®</sup> hex sets – 6 inch sizes and 6 metric sizes	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	blue	.30
70574	Grip-It® hex sets – 9 inch sizes	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	yellow	.33
70575	Grip-It® hex sets – 9 inch sizes	.050",1/16",5/64",3/32",7/64",1/8",9/64",5/32",3/16"	yellow	.20

# **TORX®** Set

## Folding TORX® Set

- TORX<sup>®</sup> drive cuts slippage, saves fasteners, efficiently transmits more torque to the work.
- · Keys are tough, heat-treated chrome-nickel alloy steel for strength and durability.
- Keys fold flat into handle.
- Can be used straight out or at an angle for extra leverage.

Cat. No.	Handle Length	Blade Lengths	Contains	Weight (lbs.)
70586	4-1/4" (108 mm)	2-1/8" to 3" (54 mm to 76 mm)	T10, T15, T20, T25, T27, T30, T40	.30





TORX® is a trademark of Acument Intellectual Properties, LLC.

**AWARNING:** Always wear approved eye protection.

AWARNING: NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Do NOT use a pipe or similar extension to increase leverage.

# L-Style Hex-Key Sets

#### Features:



### L-Style Ball-End Hex-Key Caddy Sets

#### Additional Features:

- L-style hex-keys organized in convenient, durable caddy sets.
- Each set contains a unique locking feature and marked slots for each key.
- Ball-end works on angles up to 30°.

#### 12-Piece Ball-End Hex-Key Set - Inch

Cat. No.	Set Contains	Weight (lbs.)
BLK12		.53

		Size a	and Length
Cat. No.	Hex Size	Short Arm Length	Long Arm Length
BL2	.050"	19/32"	2-29/32"
BL4	1/16"	5/8"	3-1/16"
BL5	5/64"	21/32"	3-1/4"
BL6	3/32"	23/32"	3-7/16"
BL7	7/64"	3/4"	3-5/8"
BL8	1/8"	13/16"	3-13/16"
BL9	9/64"	27/32"	4"
BL10	5/32"	29/32"	4-3/16"
BL12	3/16"	1"	4-15/32"
BL14	7/32"	1-3/32"	4-7/8"
BL16	1/4"	1-3/16"	5-5/16"
BL20	5/16"	1-5/16"	6"



#### 9-Piece Ball-End Hex-Key Set - Metric

Cat. No.	Set Contains	Weight (lbs.)
BLMK10		.62

		Size and Length	
Cat. No.	Hex Size	Short Arm Length	Long Arm Length
BLM15	1.5 mm	1/2"	3"
BLM2	2 mm	5/16"	3-3/16"
BLM25	2.5 mm	2/32"	3-7/16"
BLM3	3 mm	23/32"	3-27/32"
BLM4	4 mm	29/32"	4-1/16"
BLM5	5 mm	1-1/32"	4-17/32"
BLM6	6 mm	1-3/16"	5-13/32"
BLM8	8 mm	1-11/32"	6-5/32"
BLM10	10 mm	1-1/2"	6-17/32"

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.



# L-Style Hex-Key Sets

### L-Style Hex-Key Caddy Sets

#### Additional Features:

- L-style hex-keys organized in convenient, durable caddy sets.
- Caddy contains a unique locking feature and marked slots for each key.

#### 12-Piece Hex-Key Set - Inch

Cat. No.	Set Contains	Weight (lbs.)
LLK12		.54

		Size	and Length
Cat. No.	Hex Size	Short Arm Length	Long Arm Length
LL2	.050"	5/8"	2-15/16"
LL4	1/16"	21/32"	3-3/32"
LL5	5/64"	11/16"	3-9/32"
LL6	3/32"	3/4"	3-15/32"
LL7	7/64"	25/32"	3-21/32"
LL8	1/8"	27/32"	3-27/32"
LL9	9/64"	7/8"	4-1/32"
LL10	5/32"	15/16"	4-7/32"
LL12	3/16"	1-1/32"	4-1/2"
LL14	7/32"	1-1/8"	4-29/32"
LL16	1/4"	1-7/32"	5-11/32"
LL20	5/16"	1-11/32"	6-1/32"



BL8

9-Piece Hex-Key Set - Metric

Cat. No.	Set Contains	Weight (lbs.)
LMK10		.63

Size and Le			d Length
Cat. No.	Hex Size	Short Arm Length	Long Arm Length
LLM15	1.5 mm	23/32"	3-1/8"
LLM2	2 mm	7/16"	3-1/32"
LLM25	2.5 mm	1/2"	3-9/32"
LLM3	3 mm	9/16"	3-1/2"
LLM4	4 mm	11/16"	3-31/32"
LLM5	5 mm	13/16"	4-3/8"
LLM6	6 mm	15/16"	4-27/32"
LLM8	8 mm	1-1/32"	5-1/32"
LLM10	10 mm	1-3/32"	5-9/32"

# **L-Style Hex-Keys**

### L-Style Ball-End Hex-Keys

#### Additional Features:

- Allows easy access, even in restricted areas.
- Long side for accessing hard-to-reach places.
- Short side for higher torque situations and low clearances.

		•		
		Size and Le	ngth	
Cat. No.	Hex Size	Short Arm Length	Long Arm Length	Weight (lbs.)
Ball-End Hea	x-Key – Inch			
BL2	.050"	19/32"	2-29/32"	.002
BL4	1/16"	5/8"	3-1/16"	.002
BL5	5/64"	21/32"	3-1/4"	.005
BL6	3/32"	23/32"	3-7/16"	.005
BL7	7/64"	3/4"	3-5/8"	.01
BL8	1/8"	13/16"	3-13/16"	.02
BL9	9/64"	27/32"	4"	.02
BL10	5/32"	29/32"	4-3/16"	.03
BL12	3/16"	1"	4-15/32"	.05
BL14	7/32"	1-3/32"	4-7/8"	.06
BL16	1/4"	1-3/16"	5-5/16"	.09
BL20	5/16"	1-5/16"	6"	.17
BL24	3/8"	1-7/16"	6-13/16"	.23



0

		Size and Length		
Cat. No.	Hex Size	Short Arm Length	Long Arm Length	Weight (lbs.)
Ball-End Hex-Ke	ey – Metric			
BLM15	1.5 mm	1/2"	3"	.01
BLM2	2 mm	5/16"	3-3/16"	.01
BLM25	2.5 mm	2/32"	3-7/16"	.01
BLM3	3 mm	23/32"	3-27/32"	.02
BLM4	4 mm	29/32"	4-1/16"	.03
BLM5	5 mm	1-1/32"	4-17/32"	.05
BLM6	6 mm	1-3/16"	5-13/32"	.08
BLM8	8 mm	1-11/32"	6-5/32"	.14
BLM10	10 mm	1-1/2"	6-17/32"	.24

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

EST 1857

146

**AWARNING:** Do NOT use a pipe or similar extension to increase leverage.

# L-Style Hex-Keys

### Long-Arm Hex-Keys — Inch

## 0

LL8

#### Additional Features:

- Long side for accessing hard-to-reach places.
- Short side for higher torque situations and low clearances.

		Size and Length		
Cat. No.	Hex Size	Short Arm Length	Long Arm Length	Weight (lbs.)
LL2	.050"	5/8"	2-15/16"	.005
LL4	1/16"	21/32"	3-3/32"	.005
LL5	5/64"	11/16"	3-9/32"	.005
LL6	3/32"	3/4"	3-15/32"	.01
LL7	7/64"	25/32"	3-21/32"	.02
LL8	1/8"	27/32"	3-27/32"	.02
LL9	9/64"	7/8"	4-1/32"	.03
LL10	5/32"	15/16"	4-7/32"	.03
LL12	3/16"	1-1/32"	4-1/2"	.05
LL14	7/32"	1-1/8"	4-29/32"	.70
LL16	1/4"	1-7/32"	5-11/32"	.10
LL20	5/16"	1-11/32"	6-1/32"	.18
LL24	3/8"	1-15/32"	6-27/32"	.25

# Long-Arm Hex-Keys — Metric



LLM5

#### Additional Features:

- Long side for accessing hard-to-reach places.
- Short side for higher torque situations and low clearances.

		Size and Length		
Cat. No.	Hex Size	Short Arm Length	Long Arm Length	Weight (lbs.)
LLM15	1.5 mm	17/32"	3-1/32"	.005
LLM2	2 mm	13/32"	3-7/32"	.005
LLM25	2.5 mm	11/16"	3-15/32"	.01
LLM3	3 mm	3/4"	3-7/8"	.02
LLM4	4 mm	15/16"	4-3/32"	.03
LLM5	5 mm	1-1/16"	4-9/16"	.05
LLM6	6 mm	1-7/32"	5-7/16"	.08
LLM8	8 mm	1-3/8"	6-3/16"	.15
LLM10	10 mm	1-17/32"	6-9/16"	.25

**AWARNING:** Do NOT use a pipe or similar extension to increase leverage on L-Style Hex-Keys.










Quick, easy and accurate measurements can mean the difference between a job well done and one that misses the mark. Klein offers a variety of levels and other measuring devices that will help you measure up to the task.





### Levels

#### Features:



### **Magnetic Torpedo Level**



930-9

#### Additional Features:

- Lightweight, precision-made for durability and performance.
- Convenient 9" length for use in tight spaces.
- Three acrylic vials plumb, level and 45° provide the necessary jobsite measurements.
- Magnetized strip on bottom.

Cat. No.	Overall Length	Weight
930-9	9" (229 mm)	.25 lbs. (0.12 kg)

### **Rare Earth Magnetic Torpedo Level**



931-9RE

#### Additional Features:

- Powerful rare earth magnets, 10x stronger than strip magnets, hold firmly to iron and steel surfaces.
- Three acrylic vials plumb, level and 45° provide the necessary jobsite measurements.
- Top read level window simplifies viewing in tight areas.

Cat. No.	Overall Length	Weight
931-9RE	9" (229 mm)	.42 lbs. (0.19 kg)

### **6" Electrician's Level**



931-6RE

#### Additional Features:

- Unique 3-point design holds securely to conduit.
- For use in measuring bends in conduit.
- Machined billet aluminum design.

Cat. No.	Overall Length	Weight
931-6RE	6" (152 mm)	.325 lbs. (0.15 kg)

**AWARNING:** 931-6RE and 9317RE brass bolt contains lead, a chemical known to the State of California to cause cancer, and birth defects or other reproductive harm. Wash hands after handling.

### 9" Torpedo Level



932-9RE

#### Additional Features:

- Easy to read vials set for measurements at 0, 30, 45 and 90 degrees.
- Machined billet aluminum design.

Cat. No.	Overall Length	Weight
932-9RE	9" (229 mm)	.46 lbs. (0.21 kg)



# Levels

### **Accu-Bend™ Level**



#### Additional Features:

- Ensures precise 90° bends.
- Eliminates dog legs in conduit bends.
- 3 points of contact for superior hold to conduit.
- Relaxed V-Groove accepts up to 1" conduit.
- Solid aluminium frame for extreme durability.

Cat. No.	Overall Length	Weight
9317RE	2-1/2" (64 mm)	.162 lbs (0.07 kg)



▲WARNING: 931-6RE and 9317RE brass bolt contains lead, a chemical known to the State of California to cause cancer, and birth defects or other reproductive harm. Wash hands after handling.

### 9" Torpedo Lighted Level



9330RE

#### Additional Features:

- Lights up for maximum visibility.
- 3-minute auto shut-off saves battery life.
- Includes 2 AAA batteries.
- Water and impact resistant.
- Easy to read vials set for measurements at 0, 45 and 90 degrees.
- Machined billet aluminum design.

Cat. No.	Overall Length	Weight
9330RE	9" (229 mm)	.525 lbs. (0.24 kg)







# **Tape Measures**

#### **Features:**



True zero feature

for accurate inside and outside measuring.

Large rare earth magnetic
— end hooks

for 5x the strength.

### **Tape Measures – Magnetic**



93225



Rare earth magnets are 5x stronger! Screws securely hold magnets in place.

#### Additional Features:

- First 11" (279 mm) has oversized, bold numbers (except 93275).
- Easy read fractional scale (except 93275).
- Double-sided rule for measurement while using against wall, ceiling or conduit.
- Horizontal and vertical standout for easy one person measurements.
- Shock and impact resistant case.

Cat. No.	Blade Length	Hook	Weight
93116	16' (5 m)	single	.63 lbs. (0.29 kg)
93125	25' (7.5 m)	single	.91 lbs. (0.41 kg)
93225	25' (7.5 m)	double	.94 lbs. (0.43 kg)
93275*	7.5 m (25')	double	.94 lbs. (0.43 kg)
93430	30' (9 m)	double	1.2 lbs. (0.54 kg)

<sup>\*</sup>Note: 93275 features both centimeters and inches on both sides of blade.

## **Tape Measure – 25 Feet**



#### Additional Features:

- Oversized, bold blade numbers on first 11" (279 mm) for easy reading.
- 16" stud markings and 19.2" truss markings.
- Non-magnetic single hook.
- Rubberized lock button for comfort.
- Impact absorbing case.

Cat. No.	Blade Length	Hook	Weight
93025	25' (7.5 m)	single	.84 lbs. (0.38 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Protect hands when cleaning magnetic tip. Use gloves or cloth.

**AWARNING:** Avoid magnetic contact with sensitive electronic or computer equipment.

**AWARNING:** To avoid personal injury and damage to this tool, do not allow the tape blade to retract into case at full speed.

**AWARNING:** NOT insulated. Do NOT use on live circuits.

**AWARNING:** Do NOT open case. Spring motor is under tension, and opening case may cause injury.





# **Tape Measures**

### Tape Measures - Steel with High-Visibility Case

- High-visibility, high-impact orange case makes it easy to find in a tool box, pouch and on the jobsite.
- 16" stud markings and 19.2" truss markings.
- Made in the USA.



Cat. No.	Blade Length	Width	Weight
928-16HV	16' (4.5 m)	3/4" (19 mm)	.46 lbs. (0.21 kg)
928-25HV	25' (7.5 m)	1" (25 mm)	1.00 lbs. (0.45 kg)



928-25HV

#### **Tape Measure Holders**

 Klein offers a complete selection of leather or nylon Tape Holders and Pouches.





Tape Measure	Cat No.	Description
93116, 928-16HV	5194	small leather pouch
30110, 320 10111	5707	nylon tape measure clip/holder
93025,93125	5195	medium leather pouch
93225,93275, 928-25HV	5707	nylon tape measure clip/holder
	5196	large leather pouch
93430	5707	nylon tape measure clip/holder
	5712	nylon pouch

5707

# **Folding Rules**

### Wood Folding Rules



901-6



- Black markings on yellow, with red stud center markings every 16 inches.
- Measurements are marked on both sides and both edges, and graduated to 1/16th inch.
- Riveted lock joints are designed for long wear and maintained accuracy.
- Extension slide moves under friction in a T-slot with stops at each end. (Cat. No. 905-6)

Cat. No.	Reading	Length	Weight			
900-6	inside	6' (183 cm)	.33 lbs. (0.15 kg)			
901-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)			
6-Ft. Folding Rule — with Extension						
905-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)			

Fiberglass
Folding
Rules

910-6

- Constructed of tough nylon, reinforced with glass fibers for added durability, and resistance to weather, abrasion and most chemicals.
- Positive locking joints and stainless steel spring hinges for added strength.
- Measurements are marked on both sides and both edges, graduated to 1/16th inch.
- Black markings on yellow, with red stud center markings every 16 inches.
- Engraved graduations on both sides.

Cat. No.	Reading	Length	Weight
910-6	inside	6' (183 cm)	.33 lbs. (0.15 kg)
911-6	outside	6' (183 cm)	.33 lbs. (0.15 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open case. Spring motor is under tension, and opening case may cause injury.

**AWARNING:** NEVER use on or near live electrical circuits.

**ACAUTION:** To prevent high speed rewinding, apply slight pressure with forefinger on the underside of the blade.



# **Fiberglass Tapes**

### **Woven Fiberglass Tape - Case**

- Woven fiberglass tape with moisture-proof coating of polyvinyl chloride assures durability and protects against oil or chemicals.
- Can be immersed in water without adverse effects.
- All metal parts are nickel-plated for protection against rust.
- End-hooks are permanently attached to reinforced strip.
- Case and reel are ruggedly built yet lightweight and comfortable to use.
- Tape line graduated in feet and inches to 8ths.
- Black graduating numbers and red foot markings on yellow background.
- Protective carrying case encloses tape completely.
- Tape ring tucks neatly into case opening for storage.

Cat. No.	Length	Width	Weight
946-50	50' (15 m)	1/2" (13 mm)	.80 lbs. (0.36 kg)
946-100	100' (30 m)	1/2" (13 mm)	1.20 lbs. (0.54 kg)



### **Woven Fiberglass Tape – Open-Reel**

- Woven fiberglass tape with moisture-proof coating of polyvinyl chloride assures durability and protects against oil or chemicals.
- Can be immersed in water without adverse effects.
- Black figures on a yellow background are easy to read.
- All metal parts are nickel-plated for protection against rust.
- End-hooks are permanently attached to a reinforced strip.
- Case and reel are ruggedly built, yet lightweight and comfortable to use.
- Tape line is graduated in feet and inches to 8ths.
- Graduations and numbers are black; foot markings are red.
- Contained in an open reel and is easy to handle and rewind.

Cat. No.	Length	Width	Weight
946-150	150' (46 m)	1/2" (13 mm)	1.70 lbs. (0.77 kg)







# **Fish Tapes**

#### Features:

Polypropylene case and handle offer the maximum in impact resistance.

Round inner ring design provides a smooth, surface for winding and rewinding.

Laser etched markings in 1' increments\* allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.



\*except nylon & spiral steel

#### Unique sloped handle optimizes hand

position for quick hand-over-hand rewinds.

#### **Raised fingergrips**

transfer 100% of the winding power from your hand and fingers.

Available in steel, fiberglass and nylon with a wide variety of tips.



#### Additional Features:

- Designed for flexibility and easy navigation through conduit runs.
- Non-conductive, fiberglass fish tape slides easily over existing wires and through multiple bends.
- Durable 7" leader helps push through crowded conduit.
- The lightweight and strong fiberglass composite tape resists harsh elements and is strength rated up to 500 pulling pounds.
- Repair kit (Cat. No. 56115) available to replace tips.
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available.





1' permanent laser etched descending increments.





0		1	
•		- 1	

Cat. No.	Tape Size	Reel Diameter	Weight			
56009	50' L x 3/16" W (7" leader) (15 m L x 4.8 mm W)	13" (330 mm)	2.8 lbs. (1.27 kg)			
56010	100' L x 3/16" W (7" leader) (30 m L x 4.8 mm W)	13" (330 mm)	3.5 lbs. (1.59 kg)			
56014	200' L x 3/16" W (7" leader) (60 m L x 4.8 mm W)	17" (432 mm)	6.2 lbs. (2.81 kg)			
Replacement Parts						
56115	fiberglass fish tape repair kit		2.18 lbs. (0.1 kg)			
56116	replacement eyelets		.06 lbs. (0.03 kg)			
56120	replacement flexible leaders		.11 lbs. (0.05 kg)			



56115

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never remove screws while fish tape is coiled inside reel.

AWARNING: NEVER use on or near live electrical circuits.



# **Fish Tapes**

### **Non-Conductive Fiberglass Fish Tape**

#### Additional Features:

- Non-conductive fish tape and eyelet tip offer added protection against shock from energized sources.
- Protects existing wires from damage when fishing.
- Eyelet slides easily over existing wires and through multiple bends.
- The lightweight, strong fiberglass tape is strength rated for up to 500 pulling pounds and provides greater pushing power.
- Exclusively designed eyelet incorporates a wire trough that allows you to lay wire in eyelet making head smaller and easier to navigate through packed pipe.
- Repair kit (Cat. No. 56025) available to replace non-conductive tips.
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available.



1' permanent laser etched descending increments.

Cat. No.	Tape Size	Reel Diameter	Weight		
56024	100' L x 3/16" W (30 m L x 4.8 mm W)	13" (330 mm)	2.8 lbs. (1.27 kg)		
Replacement Parts					
56025	non-conductive fiberglass fish tape repair kit		.03 lbs. (0.01 kg)		





56025

### **Nvlon Fish Tapes**

#### Additional Features:

- Designed for flexibility and easy navigation through conduit runs.
- Non-conductive fish tape slides easily over existing wires and through multiple bends.
- The lightweight and strong nylon tape resists harsh elements and is strength rated up to 200 pulling pounds.





Cat. No.	Tape Size	Reel Diameter	Weight
56011	50' L x 3/16" W (15 m L x 4.8 mm W)	13" (330 mm)	2.3 lbs. (104 kg)
56012	100' L x 3/16" W (30 m L x 4.8 mm W)	13" (330 mm)	3.0 lbs. (1.36 kg)





## **Spiral Steel Fish Tapes**

#### Additional Features:

- Designed for super flexibility and easy navigation through conduit runs.
- Slides easily over existing wires and through multiple bends.
- The durable spiral steel tape construction yields a maximum pulling force of up to 500 lbs.





Cat. No.	Tape Size	Reel Diameter	Weight
56013	50' L x 3/16" W (15 m L x 4.8 mm W)	13" (330 mm)	5.1 lbs. (2.31 kg)



56013

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never remove screws while fish tape is coiled inside reel.

**AWARNING:** NEVER use on or near live electrical circuits.



# **Fish Tapes**

### 1/8" Wide Steel Fish Tapes

#### Additional Features:

- High strength spring steel fish tapes are stiff for long runs and are great for heavy duty wire pulls.
- Full grip style handle gives you a firm, steady grip as you pull tape from the case.
- Stainless Steel fish tape (Cat. Nos. 56007, 56008) is corrosion resistant and extends the life of the tool.



1' permanent laser etched descending increments.



Cat. No.	Tape Size	Reel Diameter	Weight			
Stainless St	Stainless Steel for corrosion resistance					
56007	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7 lbs. (2.13 kg)			
56008	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5 lbs. (3.40 kg)			
Flat Steel						
56000	25' L x 1/8" W x .045" H (7 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.0 lbs. (0.45 kg)			
56001	50' L x 1/8" W x .045" H (15 m L x 3 mm W x 1.1 mm H)	7" (178 mm)	1.3 lbs. (0.59 kg)			
56002	65' L x 1/8" W x .062" H (19 m L x 3 mm W x 1.5 mm H)	9" (229 mm)	2.6 lbs. (1.18 kg)			
56003	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	4.7 lbs. (2.13 kg)			
56004	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	13" (330 mm)	7.5 lbs. (3.40 kg)			
Replacemen	nt Tapes					
56065	65' L x 1/8" W x .062" H (19 m L x 3 mm W x 1.5 mm H)	_	1.7 lbs. (0.77 kg)			
56125	125' L x 1/8" W x .062" H (38 m L x 3 mm W x 1.5 mm H)	_	3.3 lbs. (1.50 kg)			
56240	240' L x 1/8" W x .062" H (73 m L x 3 mm W x 1.5 mm H)	-	6.1 lbs. (2.77 kg)			

### 1/4" Wide Steel Fish Tapes

#### Additional Features:

- Tempered, high quality tape keeps its stability as it glides between surfaces for effective pushing and pulling of wire under carpets, through insulated walls and over suspended ceilings.
- 25' length with no snag tip, is perfect for short wire runs associated with light commercial, residential and voice-datavideo-audio installations (Cat. No. 56005).



56005 has a no snag plastic tip



1' permanent laser etched descending increments.



56005

Cat. No.	Tape Size	Reel Diameter	Weight
56005	25' L x 1/4" W x .030" H (7 m L x 6.3 mm W x .7 mm H)	7" (178 mm)	1.1 lbs. (0.50 kg)
56006	100' L x 1/4" W x .062" H (30 m L x 6.3 mm W x 1.5 mm H)	13" (330 mm)	6.8 lbs. (3.08 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never remove screws while fish tape is coiled inside reel.

**AWARNING:** NEVER use on or near live electrical circuits.



# **Fish Tape Accessories**

#### **Fish Tape Puller**

- Exclusive design improves your grip while pulling round-diameter, composite fish tapes.
- Flexible rubberized construction is comfortable in your hand and provides excellent leverage.
- Interlocking teeth molded into channel wrap completely around the tape when squeezed.
- Fits conveniently into center of 13" fish tape case for easy storage.
- Compatible with nylon, fiberglass and spiral steel tapes.

Cat. No.	Length	Weight
56106	7-3/4" (196 mm)	.6 lbs. (0.27 kg)





56106

### 13" Flexible Leader for Steel Fish Tapes



- For use with 1/8" wide steel fish tapes.
- Heavy duty construction is strength rated up to 500 pulling pounds.
- High capacity eyelet holds up to five #12 unstripped wires and seven #10 bare wires.

Cat. No.	Length	Diameter	Weight
50350	13-1/2" (343 mm)	3/16" (5 mm)	.10 lbs. (0.04 kg)



- The 3/16" diameter tape has a rustproof inner steel cable core wrapped with a spiral cover for exceptional flexibility.
- Flexible leader guides steel tapes through 90° bends and makes pulling and pushing flat steel tapes easier.

50350

56107

## 6 Loop Wire Pulling Leader



- Save time by attaching leader to the end of a fish tape and pull up to 6 wires at once.
- Braided steel construction provides up to 450 lbs. pull strength on main eyelet.
- Flexible construction allows for easy navigation through multiple bends in conduit.
- Staggered loop lengths won't overlap and clog pipe.
- For use with 1/8" and 1/4" flat steel fish tapes.

Cat. No.	Length	Weight
56107	11-1/4" (285 mm)	.2 lbs. (0.09 kg)

### **Steel Fish Tape Puller**

- Exclusive design improves your grip while pulling all types of flat steel fish tape.
- Rugged metal construction is comfortable in your hand and provides excellent leverage.
- Internal resistance mechanism securely locks fish tape in place for pulling.
- Compatible with 1/8" & 1/4" tape widths and thicknesses of .045", .062" and .030".
- Compact size fits easily in your pocket or a tool pouch.



50355

Cat. No.	Length	Weight	
50355	3-1/4" (83 mm)	.33 lbs. (0.15 kg)	

### **Steel Fish Tape Swivel Eyelet**

- For use with 1/8" wide steel fish tapes.
- Swivel head design helps prevent kinks and allows smoother, easier fishing in tight turns.
- High capacity eyelet holds up to five #12 unstripped wires or seven #10 bare wires.
- High strength steel construction allows for optimal performance over repeated uses.
- Retrofit instructions included.



50351

Cat. No.	Length	Diameter	Weight
50351	1-1/2" (38 mm)	3/16" (5 mm)	.03 lbs. (0.01 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never remove screws while fish tape is coiled inside reel.

**AWARNING:** NEVER use on or near live electrical circuits.



# **Fish Tape Accessories**

### Fiberglass Fish Tape Repair Kit

- Contains high leverage ratcheting crimper, two replacement eyelets, two 7" replacement leaders, one tube of quick dry glue and comprehensive instructions.
- Multi-function ratcheting crimper (Cat. No. 56115V) cuts tape cleanly, strips tapes and crimps on new attachments.
- Newly crimped on eyelets meet or exceed original factory pulling strength requirements.
- Protective carry case firmly holds all tools and additional parts in handy, organized compartments.

Cat. No.	Set Contains	Weight
56115	high leverage crimper ( 1 ea.), 7" flexible leader (2 ea.), eyelets ( 2 ea.), tube quick-drying glue (1 ea)	2.18 lbs. (0.1 kg)



56115

56116

### 2-Pack 7" Replacement Flexible Leaders & 6-Pack Replacement Eyelets

- For use only with fiberglass fish tapes (Cat. No. 56009, 56010 & 56014).
- Not compatible with nylon fish tapes (Cat. No. 56011 & 56012).
- Attach with Klein Tools ratcheting crimper (Cat. No. 56115V) available in kit 56115 only.

Cat. No.	Length	Weight
56120	8.94" (227 mm)	.11 lbs. (0.05 kg)
56116	1.5" (38 mm)	.06 lbs. (0.03 kg)





# Fish Rods & Accessories

#### **Fish and Glow Rods**


- Exclusive Splinter Guard<sup>™</sup> protection from painful fiberglass splinters
- Variety of flexibilities and lengths for any application such as walls, drop ceilings, attics, crawl spaces, etc.
- LO flex long, straight feeding; HIGH flex tight bends in walls;
   MID flex all needs in between
- Luminescent glow rods provide added visibility in dark work spaces.
   Shines 2X brighter and lasts 2X longer than ordinary glow rods.
- Rods have threaded beveled connectors to attach to desired length and prevent snagging on obstructions.
- Sets include bull nose and hook attachments to attach and grab wires



NEW!



56325







## **Accessories**

#### **Illuminated Fish Rod Tip**

- · Lights up for maximum visibility in dark spaces.
- Bright white, omni-directional LED light for long life.
- Tapered end for easy pushing and pulling.
- Threaded top for hook or bullet nose attachment (not included).
- Fits drilled holes as small as 5/8".
- Compatible with 1/4", 3/16" and 5/32" diameter rods.
- Replaceable batteries included.



56119

Cat. No.	Description	Dimensions	Weight
56119	illuminated fish rod tip	2.5 " L x 37/64 " diameter	5.0 oz. (142 g)

#### **Fish Rod Accessories**

Cat. No.	Description	Set Contains	Weight
56104	3-piece fish and glow rod attachment set	(1 ea.) whisk attachment (1 ea.) bullet nose attachment (1 ea.) hook attachment	.2 oz. (5.7 g)
50992	hook and bullet nose replacements	n/a	.32 oz. (9.1 g)



- Attachments help guide, grab, attach and steer wire or cable.
- Compatible with 1/4", 3/16", and 5/32" rod sizes.

# $\textbf{Extension Pole - WireSpanner}^{\text{TM}}$



56105

- Push/Pull wires over long spans of suspended ceilings, sub-floors, crawl spaces and attics.
- The durable 54" pole quickly and easily telescopes to a maximum of 22' long.
- Each section locks securely into place and will not spin loose or collapse.
- High quality, rigid fiberglass is sturdy, lightweight and slides easily over obstructions.
- Large capacity hook-skid tip pulls multiple wires easily and has a separate eyelet for wire tie-on.

Cat. No.	Description	Collapsed Length	Extended Length	Max. Diameter	Weight
56105	WireSpanner™ installation tool	54" (1.3 m)	22' (6.7 m)	2" (50 mm)	4 lbs. (1.8 kg)
56118	WireSpanner™ carry case	-	-	-	0.4 lbs. (0.2 kg)





All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never remove screws while fish tape is coiled inside reel.

**AWARNING:** NEVER use on or near live electrical circuits.

**AWARNING:** Use a safe work position to avoid loss of balance.

# **Wire Pulling Lubricant**

### **One-Quart Premium Synthetic Clear Lubricant**

- Designed for use primarily in finished workspaces (i.e. around painted walls and carpeted floors).
- The crystal clear formulation is easy to clean-up and will not stain.
- Excellent all purpose lubricant for electrical or datacom applications.
- Compatible with most types of cable jackets.
- Temperature stable will not separate out in hot environments for when exposed to freezing.

Cat. No.	Container	Temperature Use Range	Weight
51028	one-quart squeeze bottle	20° F to 120° F (-5° C to 50° C)	2.3 lbs. (1.04 kg)





51028

### **Premium Synthetic Wax®**

- High performance lubricant for general electrical and utility applications.
- Temperature stable and does not liquify and drop off after high temperature exposure.
- Ompatible with most types of cable, including low density polyethylene.
- Superior "clingability" coats wires and conduit evenly.
- Exceptional lubricity.
- Non-staining, slow-drying, easy clean-up formula.

Cat. No.	Container	Temperature Use Range	Weight
51010	one-quart squeeze bottle	20° F to 122° F (-6° C to 50° C)	2.3 lbs. (1.0 kg)
51012	one-gallon pail	20° F to 122° F (-6° C to 50° C)	8.8 lbs. (3.9 kg)
51013	five-gallon pail	20° F to 122° F (-6° C to 50° C)	44 lbs. (19.9 kg)
56117	one-quart squeeze bottle - 6 pack	20° F to 122° F (-6° C to 50° C)	13.5 lbs. (6.12 kg)





51012



## **Premium Synthetic Polymer®**

- Excellent all-purpose lubricant for electrical, telecommunications and data applications.
- · Easy-to-apply gel clings instantly to the cable for easy handling and application.
- Compatible with most types of cable, including polyethylene and semi conducting jackets.
- Superior "clingability" coats wires and conduit evenly.
- Non-staining, slow-drying, easy clean-up formula.

Cat. No.	Container	Temperature Use Range	Weight (lbs.)
51015	one-quart squeeze bottle	20° F to 140° F (-6° C to 60° C)	2.3 lbs. (1.1 kg)
51017	one-gallon pail	20° F to 140° F (-6° C to 60° C)	8.8 lbs. (3.9 kg)
51018	five-gallon pail	20° F to 140° F (-6° C to 60° C)	44 lbs. (19.9 kg)



51015

51017



CERTIFIED TO CSA STANDARD C22.2 NO. 249-96

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Do not use wet product on live circuits. Compound is electrically conductive before it dries.





# **Wire Pulling Supplies**

### **Poly Pull Line**

- Use polypropylene line with manual or power fishing systems for light duty cable or rope pulling applications.
- Ready to use storage containers quickly dispense a tangle free line and also protects line from direct sunlight.
- Line is resistant to rot and mildew.
- Up to 210 lbs. average breaking strength.

Cat. No.	Description	Container Type	Weight
56108	500' (152 m) poly pull line with orange tracer	one-quart size w/locking lid	1 lbs. (0.45 kg)
56110	6500' (1981 m) poly pull line with orange tracer	five-gallon bucket	11 lbs. (4.9 kg)



56110

# **Conduit Tools**

#### Side-Cutting Pliers — Fish Tape Pulling

- Quickly and easily pulls 1/8" or 1/4" flat-steel fish tape without damaging the tape.
- High leverage design. Rivet is closer to the cutting edge for greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.



Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight	
D213-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	dark blue	1.1 lbs. (0.5 kg)	
Journeyman S	Journeyman Series – Dual-material handles									
J213-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	dark blue/black	1.1 lbs. (0.5 kg)	
2000 Series* -	- Heavy-duty	cutting knives								
D2000-9NETP	New England	9-3/8" (238 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	plastic-dipped	royal blue	1.1 lbs. (0.5 kg)	
Journeyman 2	000 Series* -	- Dual-material h	nandles							
J2000-9NETP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	light blue/black	1.1 lbs. (0.5 kg)	
J2000-9NECRTP	New England	9-1/2" (241 mm)	1-19/32" (41 mm)	1-1/14" (32 mm)	5/8" (16 mm)	25/32" (20 mm)	Journeyman	blue/black	1.1 lbs. (0.5 kg)	
*Cuts ACSR sc	*Cuts ACSR screws pails and most hardened wire Features combination polished and black-oxide finish									

### Conduit Pliers — Locknut and Reaming

- Tightens 1/2" (13 mm) and 3/4" (19 mm) EMT or 1/2" (13 mm) rigid locknuts.
- Fits liquid tight fittings and caps.
- Reams and smooths both inside and outside of conduit.
- Knurled jaws at nose tip pull wire or fish tape.
- Machined nose fits snugly into locknut wings.



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Point Thickness	Handle Finish	Handle Color	Weight
D333-8	7-3/4" (197 mm)	1-5/8" (41 mm)	15/16" (24 mm)	1/2" (13 mm)	3/16" (4.8 mm)	plastic-dipped	yellow	.55 lbs. (0.25 kg)

## **Conduit-Fitting and Reaming Screwdriver**

- Hooded-blade design keeps tip from slipping out of screws. especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use.
- Reams and smooths 1/2" (13 mm), 3/4" (19 mm), and 1" (25 mm) thin-wall conduit ends to protect wire and permit correct installation of fittings.

Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight
85191	3/8" (10 mm)	2-1/2" (64 mm)	7-1/2" (191 mm)	.55 lbs. (0.25 kg)
19353	conduit reamer repla	cement blade kit		.01 lbs. (0.004 kg)



85191

- Reams both the inside and outside of the conduit at the same time.
- Longer Cushion-Grip handle provides comfort and more torque for reaming.

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

### **Conduit Benders**

#### Features:



#### **Aluminum Conduit Benders**

multiplier scales and center of bend marks help save time on the job.

#### Additional Features:

Cat. No.

56206

56207

· Lightweight die-cast aluminum construction.



56207

MADE IN USA

### **Iron Conduit Benders**

#### Additional Features:


 High strength steel handle features a swaged end for inserting conduit to correct overbends (Cat. Nos. 56203 & 56204 only).

the jobsite.









All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.





## **Conduit Bender Handles**

#### **Bender Handles**



- Available in multiple sizes and lengths and are compatible with all Klein Tools conduit bender heads.
- High-strength steel eliminates flex and provides excellent feel, control and leverage.
- Handle features an enlarged diameter hollow end for inserting conduit to correct overbends (Cat. No. 51427).
- Bright orange color is easy to spot on the jobsite.

Cat. No.	Description:	Weight
51427	conduit bender handle - 38" L, 3/4" NPT tap size fits 1/2" and 3/4" bender heads and is replacement handle for #56208 and #56209.	3.5 lbs. (1.6 kg)
51428	conduit bender handle - 44" L, 1" NPT tap size fits 1" bender head for #56210.	6.0 lbs. (2.7 kg)
51429	conduit bender handle - 54" L, 1-1/4" NPT tap size fits 1-1/4" bender head for #56211.	8.9 lbs. (4.0 kg)

### **Armored Cable Cutter**

#### **BX and Armored Cable Cutter**

- Cuts BX and 3/8" armored cable.
- Eliminates burrs.
- Does not nick cable.
- Easily cuts 3/8" flexible conduit and #10, 12, and 14 armored cables with up to 4 wires with a couple of turns of the handle.
- Depth of cut adjusts between standard MC and reduceddiameter MC.
- Extra blade storage in handle.
- Use with Klein Tools replacement blade Cat. No. 53726 or 53726-SEN.

Cat. No.	Length	Weight
53725	7-1/4" (184 mm)	2.0 lbs. (0.9 kg)
Replacement Parts		
53726	Replacement blade for use with Klein Tools cable cutter Cat. No. 53725 or Cat. No. 53725-SEN.	0.1 lbs. (0.04 kg)





53725

# **Conduit Scoring Tool**

### **Electrician's Conduit Scoring Tool**

- Durable zinc cast scoring tool eliminates spiraling
- Used for scoring 1/2", 3/4" and 1"EMT conduit.
- Klein-designed, patented scoring wheel scores and allows clean conduit snaps without leaving burrs inside.
- 1" scoring wheel conveniently located in base of the handle; no tools required to replace scoring wheels.
- Four roller tracks specifically designed for professional use.
- · Compact, enclosed design for use on job sites.

Cat. No.	Length	Conduit Diameter	Weight				
88906	6.02" (153mm)	scores 1/2", 3/4" and 1" EMT conduit	1.25 lbs. (0.6 kg)				
Replacement Parts							
88907		1/2" and 3/4" EMT replacement scoring wheel					
88908		1" EMT replacement scoring wheel					





88908

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NEVER use on or near live electrical circuits.





# **PVC-Cutters**

#### **PVC-Cutter**

- Cuts up to 3/4" schedule 40 PVC.
- Makes clean burr-free cuts in PVC and flexible pipe.
- Reversible blade doubles life.
- Cuts 1-3/8" outer diameter flexible plastic pipe.
- Steel construction for strength.
- Guide helps cut pipe squarely.
- Handle latch keeps tool closed.

Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight					
50506	3/4" (19 mm) schedule 40	1" (19 mm)	8-1/2" (215 mm)	1.0 lbs.(0.45 kg)					
Replace	Replacement Parts								
50549	replacement blade		3-1/4" (83 mm)	.08 lbs. (0.03 kg)					



### **Ratcheting PVC-Cutter**

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Easy one-hand cutting.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.
- Hooked jaw holds pipe in proper cutting position.

Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight					
50500	1/2" - 1-1/4"	1" (19 mm)	9" (229 mm)	1.1 lbs. (0.5 kg)					
Replacei	Replacement Parts								
50503	replacement blade		4" (102 mm)	.19 lbs. (0.08 kg)					
50511	replacement spring		2-3/8" (60 mm)	.006 lbs. (0.002 kg)					



### **Large Capacity Ratcheting PVC-Cutter**

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.
- Handle latch keeps tool closed.



Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight
50501	1/2" – 2"	1" (19 mm)	16-1/2" (419 mm)	2.6 lbs. (1.2 kg)
Replacei	ment Parts			
50504	replacement blade		5-3/4" (146 mm)	.53 lbs. (0.24 kg)
50512	replacement spring		2-3/8" (60 mm)	.01 lbs. (0.004 kg)

50501

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NEVER use on or near live electrical circuits.

**AWARNING:** Do NOT use to cut metalic pipes or cable wire.

**AWARNING:** Do NOT cut cold PVC.













# **Protective Eyewear**

Impact resistant polycarbonate lenses block greater than 99.9% of harmful UVA and UVB radiation up to 400 nanometers.

Permanently bonded Uvextreme® anti-fog coating with anti-scratch, anti-static and UV protection properties.

Adjustable spatulite temples provide a comfortable customized fit.

Temple-end holes for easy lanyard attachment.

Wrap-around lens with integrated side shields provides a clear, unobstructed field of vision and superior coverage.

Meets the traffic signal color recognition requirements of ANSI Z80.3-1996.







#### **Lens Color**









Amher

Uvextreme® and Spectrum Control Technology® (SCT®) are registered trademarks of Sperian Eye & Face Protection, Inc.

\*SCT® = Spectrum Control Technology



#### **Protective Evewear – Standard**

#### Additional Features:

- Meets Mil V<sub>0</sub> ballistic test for impact.
- Soft elastomer brow-guard absorbs, diffuses and deflects impact energy.
- Soft flexible fingers adjust and conform to most nasal profiles reducing slippage.
- Three position ratchet lens inclination adjusts for a custom fit and unsurpassed comfort.
- Lens designed to follow the contour of the cheekbone and create a "zone of protection."
- Dual 9-base wrap-around lens provides uncompromised peripheral vision.
- Unique ventilation channel delivers an outstanding level of moisture and fog control.



Cat. No.	Frame Color	Lens Color	Environment	Light Intensity	True Color Recognition	Visual Light Transmitted	IR Absorption	Blue Light transmittance	Accidental Arc Protection	Weight (oz.)
60046	black	dark gray	outdoor	normal to bright	Yes	10%	60%	-	No	2.4
60047	black	SCT* gray	outdoor	normal to bright	Yes	15%	>85%	<7%	Yes	2.4
60049	black	amber	indoor/ outdoor	normal to low	No	90%	-	-	No	2.4
60053	black	clear	indoor	normal to low	Yes	92%	-	-	No	2.4
60054	royal blue	clear	indoor	normal to low	Yes	92%	-	-	No	2.4
60055	black	espresso	outdoor	normal to bright	Yes	15%	60%	<3%	No	2.4

### **Protective Eyewear - Frameless**

#### Additional Features:

- Meets military V0 ballistic test for impact (7x greater than ANSI).
- Secure wrap-around brow expands to fit a wide range of users.
- Ultra lightweight design offers ultimate comfort at less than one ounce.
- Proprietary Floating Lens offers increased flexibility in fit.
- Soft temple tip pads provide a comfortable and secure fit.
- Does not have lanyard holes.

to and/or packed with the product.



Cat. No.	Frame Color	Lens Color	Environment	Light Intensity	True Color Recognition	Visual Light Transmitted	IR Absorption	Blue Light transmittance	Accidental Arc Protection	Weight (oz.)
60056	black	clear	indoor	normal to low	Yes	92%	_	-	No	.15
60057	black	espresso	outdoor	normal to bright	Yes	15%	60%	<3%	No	.15

**AWARNING:** It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached





# **Personal Protective Equipment**

#### **Full Face Shield**

- Free-floating ratchet head gear with full-tension adjustment and sweat band for added comfort.
- High-impact, full-front cap and chin guard for extra protection.
- Anti-warp design resists dimensional distortion from heat and moisture.
- Big window extends past ears, providing wide-angle protection.
- Window is made of clear, tough acetate.
- Meets ANSI Z87.1-2003 and CSA Z94.3.

Cat. No.	Description	Weight (lbs.)
60060	window dimensions: 19-1/2" W x 6-1/2" H (495 mm x 165 mm)	1.45

All dimensions are in inches and (millimeters).



### **Disposable Dust Masks**

- Comfortable, full-size mask keeps dust out, lets air in freely for dependable protection and easy breathing.
- For use around grinding and sanding operations, drilling in plaster or cement, cleaning dusty areas, and similar applications.
- Double-absorbent filter material is non-allergenic.
- Elastic band and soft, flared edges make for a comfortable fit.
- Metal nosepiece conforms to fit snugly around facial contours.
- Mask stands out away from nose and mouth, and won't collapse when wet from use or humidity.

Cat. No.	Description	Weight (lbs.)
60080	box of 50 disposable dust masks	.01

**AWARNING:** These masks are NOT SUITABLE for use against toxic or hazardous air contaminants. If there is any doubt, consult an industrial hygienist.



### **Hard Caps and Accessories**

- High-density polyethylene hard caps meet ANSI Z89.1–2003 specifications for Class E.
- Unique nape strap holds hat firmly in place.
- Washable, shrink-and stretch-proof straps and bands.
- Porous brow pad promotes ventilation for comfort.
- Standard size fits head sizes 6 8.
- Full 6-point ratcheting suspension.
- Headband clips help hold goggles in place over eyes or on front of cap.
- · Rain trough helps keep neck dry.
- Slots at sides for attaching Cat. No. 60060 face shield and other protective gear. Requires 61970 universal slot adapter.

Cat. No.	Description	Color	Weight (lbs.)
60009	Hard cap	white	.85
60010	Hard cap	yellow	.85
60011	Hard cap	blue	.85



Cat. No.	Description	Weight (lbs.)
Hoodliner		
60015	winter hard-cap liner, one size fits all	.15
Face Shield		
60060	full face shield	1.45

**AWARNING:** It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.



# **Hard Hats & Caps**

### V-Gard® Cap and Hat

- Polvethylene shell with 4-point Fas-Trac<sup>®</sup> ratcheting suspension.
- Standard size fits head sizes 6 8.
- Cap and Full-Brim Hat style available.
- Three branding choices: plain front, Klein Tools Lineman Logo, Klein Tools Standard Logo.
- Three color choices: White and Blue.
- Type I helmet meets or exceeds ANSI Z89.1-2003 and CSA Z94.1-2005 specifications for Class E.
- Third Party Certified by Safety Equipment Institute.
- Full line of accessories designed specifically for the V-Gard® Cap and Hat are available.









V-Gard® and Fas-Trac® are registered trademarks of MSA, the safety company.

Front Logo		nor	ne		EST.	' /		KLEI TOOI	IN LS.
Style	Cat. No	Color	Weight (lbs.)	Cat. No.	Color	Weight (lbs.)	Cat. No.	Color	Weight (lbs.)
	60018	blue	.86	60019	white	.86	60022	white	.86
Load	00010	bluc	.00	60021	blue	.86	00022	Willie	.00
	60028	white	.95	60031	white	.95	60034	white	.95
200	60030	blue	.95	60033	blue	.95	60036	blue	.95
	All V-Gard I	helmet backs	contain the Klein logo	with American	flag (pictured	blue hard hat in squa	re). Logo color	varies depend	ling on shell color.

### Advance® Cap

- Vented style provides cooling vents for improved air circulation and comfort.
- Glaregard™ under the brim reduces reflective glare.
- Lateral contours above the ear for easy integration of hearing protection.
- Polyethylene shell with 4-point Fas-Trac® ratcheting suspension.
- Lightweight design for added comfort.
- Standard size fits head sizes 6 8.
- Branding: Plain front with Klein Tools Logo and American Flag on the back of the cap.
- Type I helmet meets or exceeds ANSI Z89.1-2003 and specifications for Class C.
- Third Party Certified by Safety Equipment Institute.
- Full line of accessories designed specifically for the Advance® Cap.

Cat. No.	Color	Weight (lbs.)
60025	white	.84
60027	blue	.84



Available in two colors







#### Scope of Z89.1 - 2003 American National Standard for Head Protection

The most recent standard was approved in July 2003 and continues to cover requirements for two types of impact-resistant helmets:

TYPE I (Top Impact) Helmets intended to reduce the force of an impact to the top of a wearer's head.

TYPE II (Top and Lateral Impact) Helmets intended to reduce the force of an impact resulting from a blow received off-center or to the top of a wearer's head. The new standard's performance requirements for Type I and Type II Helmets are equivalent to those specified in the 1998 revision.

CLASS E (Electrical) Helmets intended to reduce the danger of exposure to high-voltage electrical conductors, proof-tested at 20,000 volts.

CLASS G (General) Helmets intended to reduce the danger of exposure to low-voltage electrical conductors, proof-tested at 2,200 volts.

CLASS C (Conductive) Helmets not intended to provide protection from electrical conductors. The electrical performance requirements in the 2003 standard are identical to those in the 1997 standard.

**AWARNING:** It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.



# **Accessories**

# V-Gard®, Advance® and Skullgard® Accessories

Cat. No.	Description	Weight (oz.)			
Defender®+	Faceshield Frames (All frames meet Z87.1-2003)				
59985	Plus Universal Foldback Frame-dielectric for caps	2.9			
Visors (All viso	Visors (All visors meet Z87.1-2003, Arc Shields meet NFPA 70E, Class 2)				
59990	Arc Shield Visor - tinted (light green) HIGH-IMPACT 10" x 20" x 0.60" propionate complete w/ chin guard, 14 Cal – Z87 Basic Impact	9.5			

Advance®, Defender®, Fas-Trac®, Skullgard®, and V-Gard® are registered trademarks of MSA. Accessories sold separately.



59990

# **Klein Kleaners® Hand Cleaning Towels**

- Simple and convenient.
- Pre-moistened towels.
- No rinsing no drying no residue.
- Powerful, yet gentle, pumice-like cleaning action.
- Quickly loosens, dissolves, and absorbs dirt and grease.
- Features a natural citrus solvent that's gentler than petroleum-based hand cleaners.

Cat. No.	Container Size	Towel Size	Weight (lbs.)
51425	72-count bucket	9" x 12" (229 mm x 305 mm)	2.45





### **Utility Gloves**

- Moisture wicking and breathable Trek Dry<sup>™</sup> stretch material on top with sponge foam and tricot lining for maximum comfort.
- Durable synthetic leather palm.
- Reinforced thumb and finger panels add protection and durability.
- Wide opening elastic cuff for easy entry.

	Medium	Large	Extra-Large	Weight
Cat. No.	40205	40206	40207	.13 (lbs.) .06 (kg)

Trek Dry™ is a trademark of Mechanix Wear, Inc.



### **Camouflage Gloves**

- Mossy Oak<sup>®</sup> Break-Up Infinity<sup>™</sup> pattern.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.
- Reinforced thumb and finger panels add protection and durability.
- Single layer, seamless palm made of durable synthetic leather for improved fit and dexterity.
- Soft molded rubber closure with hook and loop secures fit.

	Medium	Large	Extra-Large	Weight
Cat. No.	40208	40209	40210	.17 (lbs.) .08 (kg)

Trek Dry™ is a trademark of Mechanix Wear, Inc. Mossy Oak® is registered trademark of Haas Outdoors Inc.



### "Cold Weather Pro" Gloves

- Palm and fingers lined with Thinsulate<sup>™</sup> C40 with fingertip designed for improved dexterity.
- Water resistant nylon back lined with Thinsulate™ C100.
- Durable rubberized palm provides water resistance and grip with 2mm EVA foam padding for impact protection.
- 5 mm EVA foam knuckle for impact protection and comfort.
- Neoprene thumb and cuff for comfort and water resistance.
- Molded rubber closure with hook and loop secures fit.

	Medium	Large	Extra-Large	Weight
Cat. No.	40211	40212	40213	.29 (lbs.) .13 (kg)

Thinsulate™ is trademark of 3M.



40212



**AWARNING:** Not flameproof or fire retardant. DO NOT expose to open flame

### "Grip" Gloves

- Armortex<sup>®</sup> rubberized grip on the fingers with reinforced synthetic leather palms and thumb for ample grip in both wet and dry conditions.
- PORON® padding material in the palm to absorb impact and vibration.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.
- Machine washable.
- Flexible yet impact absorbing thermo plastic rubber (TPR) protects the fingers and back of the hand.
- Neoprene cuff and soft molded rubber closure with hook and loop secures fit.

	Medium	Large	Extra-Large	Weight
Cat. No.	40214	40215	40216	.29 (lbs.) .13 (kg)

Trek Dry™ is a trademark of Mechanix Wear, Inc. PORON® is a registered trademark of Rogers Corp.



### "Extreme" Gloves

- Flexible yet impact absorbing thermo plastic rubber (TPR) and EVA foam protects the fingers, knuckles and back of the hand.
- PORON® padding material in the palm to absorb impact and vibration.
- Palm and thumb reinforced with synthetic leather for extra durability.
- Breathable two-way stretch materials on top with sponge foam and tricot lining for maximum comfort.
- Rubberized fingertips for extra grip.
- Wrist closure with hook and loop secures fit.

	Medium	Large	Extra-Large	Weight
Cat. No.	40217	40218	40219	.34 (lbs.) .15 (kg)

PORON® is a registered trademark of Rogers Corp.



#### **Leather Gloves**

- Genuine professional grade leather offers the finest in protection and comfort.
- Flexible yet impact absorbing thermo plastic rubber (TPR) protects the fingers and back of the hand.
- Reinforced palm with 2mm EVA foam padding for impact protection.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.
- Machine wash and dry.
- Neoprene cuff and soft molded rubber closure with hook and loop secures fit.

	Medium	Large	Extra-Large	Weight
Cat. No.	40220	40221	40222	.30 (lbs.) .14 (kg)

Trek Dry™ is a trademark of Mechanix Wear, Inc.



**AWARNING:** Not flameproof or fire retardant. DO NOT expose to open flame

or sparks

### **Pro Utility Gloves**

- Reinforced area at base of thumb strengthens key wear area.
- Wrap around design at index finger for increase wear.
- Elastic position below heel of the hand for a snug, comfortable fit.
- Extended cuff for easier on/off.
- Sewn in hang-up loop for storage.
- Nylon synthetic suede palm is durable and washable.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40030	40031	40032	.25



40030

#### **Pro Framer Work Gloves**

- Fingerless design on thumb, index and middle finger provides increased sensitivity for handling wire connectors, screws, nails and small parts.
- Protective Thermal Plastic Rubber (TPR) finger patches.
- Elastic position below heel of the hand for a snug, comfortable fit.
- Extended cuff for easier on/off.
- Palm features slip-resistant construction for better gripping power.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40034	40035	40036	.28



### **Pro Heavy-Duty Protection Gloves**

- Fingers feature slip-resistant material for better grip and wear.
- Protective Thermal Plastic Rubber (TPR) finger patches.
- Double row padded knuckle for added protection.
- Palm features slip-resistant construction for better gripping power.
- Hook and loop cuff for secure fit.
- Extended cuff for easier on/off.
- Spandex material for increased comfort.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40038	40039	40040	.46



#### **Pro Leather Work Gloves**

- Grain goat skin palm patches for better gripping and durability.
- Double row padded knuckle for added protection.
- Hook and loop cuff for secure fit.
- Spandex material for increased comfort.
- Extended cuff for easier on/off.
- Sewn in hang-up loop for storage.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40042	40043	40044	.30



40042

#### **Utility Gloves**

- Supple, breathable, durable synthetic leather palm added for firm grip.
- Two-way stretch spandex padded top features form-fitting elasticity.
- · Reinforced thumb, index finger and fingertips add protection.
- · Concealed interior seam stitching prevents snagging.
- · Wide opening elastic cuff features an easy entry design.
- Contact points on index finger and thumb feature smooth surface for improved handling of objects.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40052	40053	40054	.25



#### **Framer Gloves**

- Fingerless design on thumb, index and middle finger provides increased sensitivity for handling wire connectors, screws, nails and small parts.
- DURA-FIT™ synthetic leather palm offers maximum comfort and durability.
- Non-slip rubberized Zeus™ Clarino® finger grippers improve grip and control.
- Lycra<sup>®</sup> panels between fingers add comfort and ventilation.
- · Easy-entry Neoprene cuff ventilates and increases comfort.
- Thermal Plastic Rubber (TPR) cuff strap with hook and loop closure.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40057	40058	40059	.28

Zeus™ Clarino® and DURA-FIT™ are trademarks of Kuraray Co., Ltd. Lycra® is registered trademark of INVISTA for premium stretch fiber and fabric.



### **Heavy-Duty Protection Gloves**

- Streamlined high-density accordion knuckle panel reduces impact.
- High profile, impact absorbing molded Thermal Plastic Rubber (TPR) finger protection.
- Non-slip rubberized Zeus™ Clarino® finger and thumb grippers and panel on heel of hand provide grip control and longer wear.
- Synthetic leather with breathable mesh side-insert finger panels for comfort and flexibility.
- Two-ply synthetic leather palm with anatomically die cut Ethylene Vinyl Acetate (EVA) foam padded impact zones.
- Thermal Plastic Rubber (TPR) cuff strap with hook and loop closure.
- Neoprene cuff allows easier access with additional wrist protection and comfort.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40062	40063	40064	.46

Zeus™ Clarino® is a trademark of Kuraray Co., Ltd.



#### **Leather Work Gloves**

- Genuine Goatskin professional-grade leather offers the finest in comfort and protection.
- Two-way form-fitting spandex top increases ventilation, comfort and fit.
- Molded Thermal Plastic Rubber (TPR) ribs offer flexible protection for back of hand and fingers.
- · Lightly padded palm for increased grip and comfort.
- · Easy-entry elastic cuff ventilates and increases comfort.
- Stretch knuckle with Ethylene Vinyl Acetate (EVA) foam padding.
- Thermal Plastic Rubber (TPR) cuff strap with hook and loop closure.

	Medium	Large	Extra-Large	Weight (lbs.)
Cat. No.	40067	40068	40069	.30



**AWARNING:** Not flameproof or fire retardant. DO NOT expose to open flame or sparks.



## **Gloves**

#### **Deerskin Work Gloves**

- · Premium deerskin, soft and form-fitting for maximum comfort.
- Gunn cut with seams away from wear surfaces.
- Inseam index finger.
- Shirred-elastic wrist back.
- Natural light-tan color.


Cat. No.	Size	Weight (lbs.)
40020	small	.20
40021	medium	.22
40022	large	.23
Lined - Pile Lining		
40016	medium	.36
40017	large	.38
40018	extra large	.41



### **Cowhide Driver's Gloves**

- Tough, durable, sueded cowhide leather.
- Easy-action thumb unique design allows leather to conform to your thumb and hand (Cat. Nos. 40003, 40004, 40006).
- Thermolite® lining for warmth (Cat. Nos. 40014 and 40015).
- Gunn cut with seams away from wear surfaces.
- · Lap-seam index finger and shirred-elastic wrist back.
- Gray color.

Cat. No.	Size	Weight (lbs.)
40003	small	.30
40004	medium	.40
40006	large	.43
40014*	large	.47
40015*	extra large	.51





## **Medium and Long-Cuff Gloves**

- Heavy sueded leather (Cat No. 40008)
- Soft, flexible, top-grain cowhide leather (Cat. Nos. 40010 and 40012).
- Leather fingers, palm, pull, and knuckle strap (Cat. Nos. 40010 and 40012).
- Gunn cut with seams away from wear surfaces.
- Wing thumb, seamless index finger, elastic wrist-back strap.
- Lined palm and fingers.
- Rubberized, waterproof, bell gauntlet cuff 5" (127 mm) long (Cat. Nos. 40010 and 40012).





Cat. No.	Size	Weight (lbs.)
40008	large – medium cuff	.48
40010	large	.59
40012	extra-large	.68

# **Gloves**

#### **Lineman Work Gloves**

- 4" Neoprene cuff with side vents.
- Soft grain leather construction with reinforced leather patches.
- Double-row padded knuckle for durability.
- Black spandex back with Klein lineman logo patch.

Cat. No.	Size	Weight (lbs.)
40080	medium	.46
40082	large	.51
40084	extra-large	.55
40086	extra-extra-large	.59

A WAR	RNINGS: These	loves are not i	intended for en	ergized electrical	Luse



#### **Electrician's Gloves**

- Durable construction allows flexibility.
- Features slip resistant construction.
- Spandex material is breathable and comfortable to wear all day.
- Constructed with a reinforced area at the base of the thumb.
- Elastic cuff for secure and comfortable fit.
- Index fingers are wrapped with slip-resistant material.
- Extended cuff for easy on/off.

Cat. No.	Size	Weight (lbs.)
40072	large	.46
40074	extra-large	.48

A WARNINGS: These gloves are not intended for energized electrical use.



# **Heavyweight Jersey Gloves**

- Soft, comfortable, general-purpose gloves.
- Made of 100% cotton jersey.
- Cat. No. 40002 has a knit wrist.
- Cat. No. 40001 has a fleece lining and an open cuff.
- Dark-brown color.

Cat. No.	Size	Weight (lbs.)
40002	fits most hand sizes	.15
40001	lined version – fits most hand sizes	.16



# **Safety Products**

### **Lockouts with Interlocking Tabs**

- Specifically designed for locking out power sources such as disconnects, switches, and panel boxes.
- Double interlocking hasp of tempered steel with patented interlocking tabs for extra security.
- Hasps are bright zinc-plated.
- Riveted construction.
- Six-hole locking bodies coated with red vinyl plastic.
- Holes will accept up to 5/16" (8 mm) diameter shackles.

Cat. No.	Closed Hasp I.D.	Weight (lbs.)
45200	1" (25 mm)	.200
45201	1-1/2" (38 mm)	.250

**AWARNING:** Use only in accordance with OSHA requirements.



45201

### **Barricade and Warning Tapes**

- Bold, black lettering on bright, long-lasting color backgrounds.
- Yellow background for CAUTION/CAUTION tape.
- Red background for CAUTION-BURIED ELECTRIC LINE tape.
- Made of tough, durable (2.5 mil) polyethylene.
- Highly resistant to acids, alkalis, and other soil components.
- Tapes are 3" (76 mm) wide, and are available in either 200' or 1000' rolls.

Cat. No.	Description	Width	Length	Weight (lbs.)
58000	CAUTION – CAUTION legend with black letters on bright-yellow background	3" (76 mm)	200' (61 m)	.900
58001	CAUTION – CAUTION legend with black letters on bright-yellow background	3" (76 mm)	1000' (305 m)	3.600
58002	CAUTION – BURIED ELECTRIC LINE legend with black letters on bright-red background	3" (76 mm)	200' (61 m)	.800
58003	CAUTION – BURIED ELECTRIC LINE legend with black letters on bright-red background	3" (76 mm)	1000' (305 m)	3.500





### 7-Pocket Tool Pouch

- Soft, pliable, white leather.
- Riveted to assure long life.
- · Heavy-duty chain tape thong securely fastened with a rivet.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5166	7	chain tape thong	tunnel	2-1/4" (57 mm)	7" x 9-1/2" (178 mm x 241 mm)	.92



### 8-Pocket Tool Pouch

- Soft, pliable, white leather.
- Roomy pouch for electricians and maintenance workers.
- Riveted and stitched for extra durability.
- Heavy-duty chain tape thong securely fastened with a rivet.
- Stainless steel clip holder accepts most tape clips up to 1-1/4" wide.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5178	8	knife snap, chain tape thong, metal tape measure holder	tunnel	2-1/2" (64 mm)	11" x 10" (279 mm x 254 mm)	1.03





### **Single-Pocket Tool Pouch**

- Leather construction.
- Perfect for carrying pliers and other tools in the hip pocket.
- Prevents wear and tearing of clothes, discomfort, and possible injury.
- Riveted to assure long life.



5111

### **Strap-Leather Bag**

- Leather construction.
- Soft, pliable cushion-leather gussets allow expansion to 3-1/4" (83 mm).
- Ventilating eyelet in bottom.



Cat.	Pockets	Overall	Weight
No.	(Total Number)	Size	(lbs.)
5111	1	4-1/2" x 7" (114 mm x 178 mm)	.23

Cat. No.	Belt Connection	Belt Capacity	Length	Width	Depth	Weight (lbs.)
5140K	latigo thongs	up to 3" (76 mm) wide	7" (178 mm)	9" (229 mm)	3-1/4" (83 mm)	.65

### **3-Pocket Utility Pouch**

- Leather construction.
- Features 1" (25 mm) reinforced gusset.
- Has 2" (51 mm) outside pockets.
- Riveted for extra durability.

Cat. No.	Pockets	Belt	Belt	Overall	Weight
	(Total Number)	Connection	Width	Size	(lbs.)
5145	3	tunnel	1" (25 mm)	5-1/4" x 7" (133 mm x 178 mm)	.46



### **4-Pocket Tool Pouch**

- Leather construction.
- Riveted and stitched for extra durability.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5119	4	knife snap	slotted	2" (51 mm)	6-1/2" x 8-1/2" (165 mm x 216 mm)	.39



### **5-Pocket Tool Pouches**

- Cat. No. 5125 is constructed of #4 canvas, leather back, pockets and loops.
- Cat. No. 5125L is constructed of leather.
- General-purpose pouches.
- Heavy-duty chain tape thong securely fastened with a rivet.
- · Riveted and stitched for extra durability.





Cat. No.	Pockets (Total Number)	Specialty Add-Ons	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5125	5	leather tape thong	loops	2-1/4" (57 mm)	7-1/2" x 8-1/2" (191 mm x 216 mm)	.63
5125L	5	leather tape thong	loops	2-1/4" (57 mm)	7-1/2" x 8-1/2" (191 mm x 216 mm)	.75

### **5-Pocket Tool Pouch**

- Leather construction.
- Riveted to assure long life.



Leath	er	
<b>Back</b>	<b>Pocket</b>	<b>Pouch</b>

- Leather construction.
- Stitched and riveted to assure long life.
- Snap loop option for belt.
- Six pockets, including scissors pocket on back flap.



Cat. No.	Specialty Add-Ons		Belt Width	Overall Size	Weight (lbs.)
5126	knife snap	slotted	2" (51 mm)	6" x 8-3/4" (152 mm x 222 mm)	.74

Cat. No.	Belt	Belt	Overall	Weight
	Connection	Width	Size	(lbs.)
5481	snap loop	up to 2" (51 mm)	10" H x 5-3/4"W x 2-1/2"D (254 mm x 146 mm x 64 mm)	.47

### **6-Pocket Tool Pouches**

- Leather construction.
- Riveted to assure long life.

Cat. No.	Pockets (Total Number)	Specialty Add-Ons	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5127	6	knife snap	slotted	2" (51 mm)	7" x 10" (178 mm x 254 mm)	.79
5127T	6	knife snap	tunnel		7" x 10" (178 mm x 254 mm)	.87







### 8-Pocket Extra-Capacity Tool Pouch

- Leather construction.
- Extra-capacity multi-purpose pouch.
- Stitched and riveted.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5162T	8	knife snap, leather tape thong	tunnel	3" (76 mm)	8-1/2" x 10-3/4" (216 mm x 273 mm)	1.71



5162T

### **8-Pocket Tool Pouches**

- Leather construction.
- Riveted to assure long life.

Cat. No.	Pockets (Total Number)	Specialty Add-Ons	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5164	8	knife snap	slotted	2" (51 mm)	6-3/4" x 9-3/4" (171 mm x 248 mm)	1.16
5164T	8	knife snap	tunnel	2-1/2" (64 mm)	6-3/4" x 9-3/4" (171 mm x 248 mm)	1.21





5164T

### **10-Pocket Tool Pouch**

- Leather construction.
- Riveted and stitched.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5165	10	knife snap	slotted	2" (51 mm)	10" x 10" (254 mm x 254 mm)	1.26





- Leather construction.
- · Versatile pouch favored by many telephone installers.
- Riveted throughout to assure long life.
- Ten separate compartments with places for a wide variety of pliers, screwdrivers, and other tools.
- Slotted-leather tape thong (allows easy removal of 1" I.D. tape rolls).

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5190	10	leather tape thong	slotted	1-3/4" (44 mm)	6" x 8-3/4" (152 mm x 222 mm)	.75





### 11-Pocket Tool Pouch

- Leather construction.
- Multi-pocketed pouch made for electricians and other professionals.
- Riveted and stitched.
- Stainless steel clip holder accepts most tape clips up to 1-1/4" wide.
- · Heavy-duty chain tape thong securely fastened with a rivet.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
5167	11	knife snap, chain tape thong, metal tape measure holder	slotted	2-3/4" (70 mm)	10" x 10-1/2" (254 mm x 267 mm)	1.43



### **Back Pocket Pouch**

- Four pockets, including two open pockets on the front for longer tools such as screwdrivers.
- Cordura<sup>®</sup> ballistic nylon, a high-performance fabric resistant to abrasions, tears and scuffs.
- Stitched and riveted to assure long life.
- Snap loop option for belt.



Cat. No.	Belt Connection	Belt Width	Length	Width	Depth	Weight
5482	snap loop	up to 2" (51 mm)	9-7/8" (251 mm)	5" (127 mm)	2" (51 mm)	.26 lbs. (0.12 kg)

Cordura® is a registered trademark of INVISTA for durable fabrics.



### **All-Purpose Bag**

- Soft, pliable cushion leather construction.
- Bag is ideal for carrying loose tools and small parts.
- Adjustable belt strap for attaching to belts.



5146	Length	Width	Depth	Weight
	4	100		5146
				24
	7			

Cat. No.		Belt Capacity	Length	Width	Depth	Weight (lbs.)
5146	belt strap	up to 3" (76 mm) wide	9" (229 mm)	8" (203 mm)	3" (76 mm)	.60

### **Leather Bolt Bag**

- Split-leather construction.
- Bolt bag with bull-pin loop on each side.



42247

Cat. No.	Belt Connection	Belt Capacity	Length	Width	Depth	Weight (lbs.)	Cat. No.	Belt Connection	Belt Capacity	Length	Width	Depth	Weight (lbs.)
5146	belt strap	up to 3" (76 mm) wide	9" (229 mm)	8" (203 mm)	3" (76 mm)	.60	42247	tunnel	up to 3" (76 mm) wide	5" (127 mm)	8-1/2" (216 mm)	8-1/2" (216 mm)	.75

### **Canvas Utility Bag**

- Heavy No. 8 natural canvas.
- Includes interior pocket.
- Inside bottom is reinforced with cushion leather & ventilating eyelet.
- Metal snaps provided on loops for easy attachment to belts up to 3" (76 mm) wide.
- Top edge reinforced with 1/4" (6 mm) rope.
- Cat. No. 5142P version includes interior pocket.

Cat. No.	Belt Connection	Belt Capacity	Length	Width	Depth	Weight
5141P	loops	up to 3" (76 mm) wide	10" (254 mm)	12" (305 mm)	5" (127 mm)	.88 lbs. (0.40 kg)
5142	loops	up to 3" (76 mm) wide	9" (229 mm)	10" (254 mm)	8" x 3" (203 mm x 76 mm)	.60 lbs. (0.27 kg)
5142P	loops	up to 3" (76 mm) wide	9" (229 mm)	10" (254 mm)	8" x 3" (203 mm x 76 mm)	.65 (0.29 kg)





5141P





### **Nut & Bolt Pouch**

- Includes interior pocket.
- Top sides of pouch reinforced with leather to maintain shape of pouch opening.
- Inside bottom is reinforced with leather and ventilating eyelet.
- Metal snaps provided on loops for easy attachment to belts up to 3" (76 mm) wide.
- Top edge reinforced with 1/4" (6 mm) rope.

Cat. No.	Interior Pockets	Color	Length	Width	Depth	Weight
51A	1	black	9" (229 mm)	10" (254 mm)	3.5" (90 mm)	1 lbs. (0.45 kg)

### **Water-Repellent Canvas Pouches**

- One-piece tan 12-oz. water-repellent mildew resistant canvas.
- Top edge reinforced with 1/4" (6 mm) rope.

Cat. No.	Belt Connection	Belt Capacity	Length	Width	Top Diameter	Weight
5179	loops	up to 4-1/2" (114 mm) wide	7-1/2" (191 mm)	3-1/2" (89 mm)	7" (178 mm)	.30 lbs. (0.14 kg)
5179S	snap	up to 4-1/2" (114 mm) wide	7-1/2" (191 mm)	3-1/2" (89 mm)	7" (178 mm)	.30 lbs. (0.14 kg)





### **Bull-Pin and Bolt Bags**

- No. 4 canvas or split-leather with double bottom.
- Bolt bag with bull-pin loop on each side.



5416TC

5416TCP



Cat. No.	Belt Connection	Belt Capacity	Length	Width	Depth	Weight
Canvas						
5416	loops	up to 3" (76 mm) wide	5" (127 mm)	9" (229 mm)	10" (254 mm)	.85 lbs. (0.30 kg)
5416T	tunnel	up to 3" (76 mm) wide	5" (127 mm)	9" (229 mm)	10" (254 mm)	.90 lbs. (0.4 kg)
Canvas -	- Top Closin	g				
5416TC	tunnel	up to 3" (76 mm) wide	5" (127 mm)	9" (229 mm)	10" (254 mm)	.87 lbs. (0.39 kg)
5416TCP	tunnel	up to 3" (76 mm) wide	5" (127 mm)	9" (229 mm)	12" (305 mm)	1 lbs. (0.45 kg)
Leather						
5416L	tunnel	up to 3" (76 mm) wide	5" (127 mm)	9" (229 mm)	10" (254 mm)	1.10 lbs. (0.14 kg)

### **Canvas Electrode Bag**

- Made of tough No. 4 canvas.
- Heat-resistant, hard leather bottom.
- Web loop for sliding over belt.



Cat. No.	Diameter	Front Depth	Back Depth	Weight (lbs.)
5471	2-1/2" (64 mm)	12" (305 mm)	15-1/2" (394 mm)	.25

### 6-Pocket Nail/Screw and Tool Pouch

- Split-leather construction.
- Heavy hammer-loops on both sides, allowing for convenient use by right- or left-handed workers.
- Riveted and stitched for extra durability.

Cat. No.	Pockets	Specialty	Belt	Belt	Overall	Weight
	(Total Number)	Add-Ons	Connection	Width	Size	(lbs.)
42241	6	2 hammer loops	tunnel	3" (76 mm)	11" x 11-3/4" (279 mm x 298 mm)	.86



42241

42242

# **Tool Combination Aprons**

### **One-Piece Nail/Screw and Tool Pouch Apron**



- Split-leather construction.
- Versatile, roomy double-pouch apron for construction workers, carpenters, and other professionals.
- Riveted and stitched for extra durability.
- Four slots for punches or nail sets.
- Two heavy-duty hammer loops.
- Double-pouch design allows unrestricted leg movement.
- Apron is reinforced throughout with rivets.
- The large pockets and nail/bolt pockets have rolled-over, doubled edges for long wear.
- Heavy-duty 2" (51 mm) wide polypropylene web belt has rugged metal buckle.

Cat. No.	Pockets (Total Number)	Size Adjustable	Weight (lbs.)
42242	10	32" – 48" (813 mm – 1219 mm)	1.81

### **Nail/Screw and Tool Pouch Combinations**

- Split-leather construction.
- Large pockets have rolled-over doubled edges for extra-long life.
- All pouches slide along belt for convenient working position.
- Left- and right-hand nail-and-tool pouches.
- Heavy-duty 2" (51 mm) wide polypropylene web belt has rugged metal buckle.
- Tape-rule holder for 20' and 25' tape measures with belt clips.
- · Heavy hammer loops.



42244

Cat. No.	Description	Weight (lbs.)
42244	complete combination: belt (Cat. No. 5225 mm), left-hand (Cat. No. 42246 mm) and right-hand (Cat. No. 42245 mm) nail-and-tool pouches, and tape-rule holder (Cat. No. 5195 mm)	2.02
42245	right-hand nail-and-tool pouch only. Tunnel loop fits any belt up to 3" (76 mm) width.	.70
42246	left-hand nail-and-tool pouch only. Tunnel loop fits any belt up to 3" (76 mm) width.	.72
5225	poly-web belt only. Adjustable from 32" (813 mm) to 48" (1219 mm). Tunnel loop fits any belt up to 3" (76 mm) width.	.42
5195	tape-rule holder only for 20' and 25' tapes.	.18

**AWARNING:** The tool belts shown on this page are not occupational protective belts





# **Tool Combination Aprons**

### **Electrician's Tool Apron**



Cat No.	Size	Fits Waist Sizes	Weight
42200	M/L	32" - 46" (813 mm - 1,168 mm)	.86 lbs. (0.39 kg)
42201	XL/2XL	38" - 54" (965 mm - 1,372 mm)	.93 lbs. (0.42 kg)

### **Tool Holders**

### Scissors Holder — Tunnel

- Leather construction.
- Designed for Klein electrician's scissors, industrial shears, snips and bent trimmers.
- Riveted and stitched for extra durability.



5100M

Cat. No.	<b>Belt Connection</b>	Belt Width	Overall Size	Weight (lbs.)
5100M	tunnel	up to 2" (50.8)	Medium	3.2

### Scissors Holder — Slotted

- Leather construction.
- Riveted with clip on back for attaching to belt.
- Designed to hold Klein electrician's scissors, Cat. Nos. 2100-5 and 2100-7.
- Riveted to assure long life.



5101

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5101	metal clip	up to 1-1/2" (38 mm)	2" x 7" (51 mm x 178 mm)	.11

### **Scissors** and Cable-Splicer's **Knife Holders**

- Leather construction.
- Specially designed to hold a pair of Klein electrician's scissors (Cat. Nos. 2100-5 or 2100-7, 2100-8, 2100-9), and Cat. No. 44200 cable-splicer's knife.
- Riveted and stitched for extra durability.



5187 5187T

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5187	slotted	up to 2-1/4" (57 mm)	2" x 7-1/4" (51 mm x 184 mm)	.11
5187T	tunnel	up to 2-1/4" (57 mm)	2" x 7-1/4" (51 mm x 184 mm)	.13

### **Lineman's Knife Holder**

- Leather construction.
- Designed for Klein skinning knives Cat. Nos. 1570-3, 1570-3LR, and 1560-3.
- Riveted to assure long life.



Cat. No.	<b>Belt Connection</b>	Belt Width	Overall Size	Weight (lbs.)
5163	slotted	up to 2" (51 mm)	3-1/2" x 9-3/8" (89 mm x 238 mm)	.21

### **Tool Holders**

### **Knife Holder**

- Leather construction.
- Designed for utility knives and Klein Cat. Nos. 44100 and 44105.
- Corners riveted and stitched for extra durability.

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5185	slotted	up to 2-1/2" (64 mm)	2-5/8" x 8-1/4" (67 mm x 210 mm)	.11



5185

### **Cable-Splicer's Knife Holders**

- Leather construction.
- Designed to hold Cat. No. 44200 cable-splicer's knife.
- Riveted and stitched for extra durability.

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5188	slotted	up to 2-1/4" (57 mm)	2-1/8" x 7-3/4" (54 mm x 197 mm)	.08
5188T	tunnel	up to 2-1/4" (57 mm)	2-1/8" x 7-1/4" (54 mm x 184 mm)	.11



5188T

### Pliers Holders - Open Bottom

- Leather construction.
- Long-nose pliers may protrude through opening at bottom.
- Riveted to assure long life.
- Cat. No. 5107-6 holds 6" (152 mm) or 7" (178 mm) long-nose or diagonal-cutting pliers.
- Cat. No. 5107-9 holds 8" (203 mm) or 9" (229 mm) long-nose or diagonal-cutting pliers.



5107-6

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5107-6	slotted	up to 2" (51 mm)	3-1/2" x 8-1/2" (89 mm x 216 mm)	.17
5107-9	slotted	up to 2" (51 mm)	3-3/4" x 11" (95 mm x 279 mm)	.26

### Pliers Holder — **Closed Bottom**

- Leather construction.
- Nose of pliers does not protrude from closed bottom.
- Bottom is vented to prevent collection of dirt or water.
- Riveted to assure long life.
- Holds 7", 8", or 9" side-cutting pliers.



5112

Cat. No.	Belt	Belt	Overall	Weight
	Connection	Width	Size	(lbs.)
5112	slotted	up to 2" (51 mm)	3-1/4" x 11" (83 mm x 279 mm)	.21

### Pliers, Folding Rule, Screwdriver, and **Wrench Holder**

- Leather construction.
- No exposed rivets in back.
- Riveted to assure long life.
- Pockets for 7", 8", and 9" sidecutting pliers, most screwdrivers, 6' folding rules, and open-end wrenches from 9/16" to 13/16".
- Nickel plated alloy snap.



5118C

Cat.	Pockets	Belt	Belt	Overall	Weight
No.	(Total Number)	Connection	Width	Size	(lbs.)
5118C	4	slotted	up to 2" (51 mm)	6-1/2" x 11" (165 mm x 279 mm)	.78

### Pliers, Rule, and **Screwdriver Holders**

- Leather construction.
- 3 pockets for pliers, folding rule, and screwdriver.
- S5118PRS has a two-way knife snap.
- Riveted to assure long life.
- Pockets for 7", 8", and 9" sidecutting pliers, most screwdrivers, 6' folding rules, and open-end wrenches from 9/16" to 13/16".



5118PRS

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5118PRS	slotted	up to 2" (51 mm)	6-3/4" x 10" (171 mm x 254 mm)	.49
S5118PRS	slotted	up to 2" (51 mm)	6-3/4" x 10" (171 mm x 254 mm)	.56



### **Tool Holders**

### 4 and 5 Pocket Pouches Lineman's Pouches

- Leather construction with double leather back for durability.
- Rivet hole for belt connection.
- Riveted to assure long life.
- Includes knife snap, pockets for pliers, most screwdrivers, 6' folding rule and open-ended wrenches.





5118P4

5118P5

Cat. No.	Pockets (Total No.)	Belt Connection	Approx. Overall Size	Weight (Ibs.)
5118P5	5	rivet hole	10" x 11" (254 mm x 279 mm)	1.13
5118P4	4	rivet hole	8" x 11" (203 mm x 279 mm)	.91

### **Pliers and Folding Rule Holders**

- Leather construction.
- Riveted to assure long life.
- Pockets for 7", 8", or 9" side-cutting pliers and 6-ft. folding rule.

Cat. No.	Pockets (Total Number)	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5118R	2	slotted	up to 2" (51 mm)	4-3/4" x 8" (121 mm x 203 mm)	.43
5118RT	2	tunnel	up to 3-3/4" (95 mm)	4-1/2" x 12-1/2" (114 mm x 318 mm)	.50





5118R

5118RT

### **Pliers and Screwdriver Holder**

- Leather construction.
- Riveted to assure long life.
- Pockets for 7", 8", or 9" side-cutting pliers and most screwdriver sizes.

Cat. No.	Pockets	Belt	Belt	Overall	Weight
	(Total Number)	Connection	Width	Size	(lbs.)
5118S	2	slotted	up to 2" (51 mm)	4-1/4" x 10-3/4" (108 mm x 273 mm)	.35



5118S

### **Hammer Holders**

- Leather construction.
- Heavy-metal hammer loop riveted to panel.
- Riveted and stitched for extra durability.
- Holds all hammers except lineman's.

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5456	slotted	up to 2-1/2" (64 mm)	4-5/16" x 7-7/8" (110 mm x 200 mm)	.33
5456T	tunnel	up to 4" (102 mm)	4-5/16" x 10" (110 mm x 254 mm)	.42
5456TS	tunnel	up to 4" (102 mm)	4-5/16" x 10" (110 mm x 254 mm)	.42







5456T 5456TS

188

### **Tool Holders**

### **Flashlight Holder**

- Leather construction.
- Designed for a standard two-cell flashlight.
- Riveted to assure long life.



5129

Cat. No.	Belt	Belt	Overall	Weight
	Connection	Width	Size	(lbs.)
5129	slotted	up to 2-1/4" (44 mm)	3" x 9-1/2" (76 mm x 241 mm)	.22

### **Cordura® Ballistic Nylon** Flashlight Holder

- Cordura<sup>®</sup> ballistic nylon for exceptional resistance to abrasions, punctures and tears.
- Metal belt clipattaches to belts up to 2" wide.
- Secure snap closure.



1106

Cat. No.	Applicable	Dimensions	Weight
	Model	H x W x D	(oz.)
1106	X35	9" x 2.75" x 1.88" (22.9 cm x 6.99 cm x 4.78 cm)	3.4

### **Tape-Rule Holders**

- Leather construction.
- Cut-out sides for easy access to tape.
- Slotted for attaching to belts up to 2-1/2" (63 mm) wide.
- Riveted to assure long life.



Cat. No.	Description	Overall Size	Weight (lbs.)
5194	small	4" x 6" (102 mm x 152 mm)	.16
5195	medium	4-1/2" x 7" (114 mm x 178 mm)	.18
5196	large	5" x 7" (127 mm x 178 mm)	.21

### Klein Tape-Rule Sizing Guide

Tape Measure	Cat No.	Description
	5194	small leather pouch
93116	5707	nylon tape measure clip/holder
93025, 93125	5195	medium leather pouch
93225, 93275	5707	nylon tape measure clip/holder
	5196	large leather pouch
93430	5707	nylon tape measure clip/holder
	5712	nylon pouch



5195

5459T

### **Erection Wrench Holder**

- Cotton web tunnel loop and leather construction.
- Holds two erection wrenches.
- Riveted to assure long life.
- Holds erection wrenches and adjustable head construction wrench Cat. No. 3239.

Cat. No.	Belt	Belt	Overall	Weight
	Connection	Width	Size	(lbs.)
5461T	cotton web tunnel	up to 2" (51 mm)	6" x 10" (152 mm x 254 mm)	.26

### **Bull-Pin Holders**

- Leather construction.
- Holders for Klein bull pins.
- Riveted to assure long life.
- Holds all standard bull pins.






5417

			5417	5417T
Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5417	slotted	up to 2" (51 mm)	3-1/4" x 11" (83 mm x 279 mm)	.22
5417T	tunnel	up to 3-1/2" (89 mm)	3-1/4" x 12-1/4" (83 mm x 311 mm)	.32

### **Erection Wrench Holders**





 Holds erection wrenches and adjustable head construction wrench Cat. No. 3239.







### **Tape Thong**

• Leather strap with fiber bar.

**Tool Holders** 

• Fits all standard electrical tape rolls.

Cat. No.	Belt Connection	Length	Weight (lbs.)
5130	slotted	12" (305 mm)	.03



### Tie-Wire Reel Pad

- Worn on the belt under the Klein tie-wire reel.
- Made of 3/16" (5 mm) thick rigging leather.
- Slots accommodate belts up to 2" (51 mm) wide.
- Underside has a sponge-rubber pad to minimize hip fatigue.
- Holds Cat. No. 27400 tie-wire reel.
- To be used with Cat. Nos. 5415 or 5420 belts.

Cat. No.	Length	Width	Weight (lbs.)
27450	7" (178 mm)	7" (178 mm)	.300

Tie-wire reel and ironworker's heavy-duty tie-wire belts also available.



27450

### **Two-Way Snap**

- Leather construction.
- Screw-type rivets for easy attachment to belts.





### **Snap Loop**

- Leather construction.
- Designed for tools with hang holes.
- Loop with snap hook for carrying an adjustable wrench, welder's igniter or other tool with hang hole.
- Riveted to assure long life.



Cat. No.	<b>Belt Connection</b>	Belt Width	Overall Size	Weight (lbs.)
5458	slides on	up to 4" (102 mm)	1-1/2" x 8-1/2" (38 mm x 216 mm)	.15

Cat. No.	Belt Connection	Length	Weight (lbs.)
5131	screw rivets	4-1/2" (114 mm)	.10

### **Tool Guards**

### **Axe Guard**



- Protect both tool and user with a Klein guard for your edged tools.
- Made of 1/16" (1.6 mm) vulcanized hard fiber, securely riveted and equipped with adjustable web straps to hold the tool.

Cat. No.	Description	Weight (lbs.)
5509	axe guard	.22

### **Splitting-Knife Guards**

Leather construction.





5574L

5574S

Cat. No.	Description	Weight (lbs.)
5574L	leather splitting or chipping-knife guard. Fits Klein knife, Cat. No. 1515-1	.13
5574S	leather splitting or chipping-knife guard. Fits Klein knife, Cat. No. 1515-S	.05

### Tradesman Pro™ Organizer – Electrician's Tool Belt



- 26 pockets for easy tool storage.
- Wide open pockets for tools, drills and spare parts.
- Removable pouches allow you to carry only the tools needed.
- Exclusive drill bit pocket.
- Handles for easy carrying.
- Loop tape measure holder.
- Padded belt with mesh interior is breathable and comfortable.
- Rugged leather belt ends.
- Attachments for Tradesman Pro<sup>™</sup> padded suspenders (Cat. No. 55400).

Cat. No.	Size	Weight
55427	31" - 34" (787 mm - 864 mm)	4.15 lbs. (1.88 kg)
55428	35" - 39" (889 mm - 991 mm)	4.16 lbs. (1.89 kg)
55429	40" – 44" (1016 mm – 1118 mm)	4.30 lbs. (1.95 kg)



Exclusive drill bit pocket

### Tradesman Pro™ Padded Suspenders

- Made of tear resistant Cordura<sup>®</sup>.
- Fully adjustable.
- Durable nylon web straps for long wear.
- Heavy duty padding for comfort.
- Easy snap hook fastening system.
- Designed for use with Tradesman Pro<sup>™</sup> Organizer electrician's tool belt (Cat. Nos. 55427, 55428, 55429).

Cat. No.	Size	Weight
55400	one size fits most	.84 lbs. (.38 kg)

Cordura® is a registered trademark of INVISTA for durable fabrics.











### Tradesman Pro™ Mobile Phone Holders

- Cat No. 55460 Fits iPhone® 4 and 5, and similar sized phones.
- Cat No. 55461 Fits Samsung Galaxy S® 3 and 4, and similar sized phones.
- Metal clip for attaching to belts up to 2" wide.
- Magnetic flap closure.
- Constructed of 1680d ballistic weave.

Cat. No.	Width	Height	Depth	Weight
55460	3.00" (76 mm)	5.75" (146 mm)	1.50" (38 mm)	0.22 lbs. (0.10 kg)
55461	3.25" (84 mm)	5.875" (149 mm)	1.50" (38 mm)	0.26 lbs. (0.12 kg)

iPhone® is a registered trademark of Apple, Inc.

Galaxy S<sup>®</sup> is a registered trademars of Samsung Electronics Co., Ltd.





55460

### **Tradesman Pro™ Carrying Cases**

- Two layers of padding protect even delicate instruments.
- Heavy-duty zipper and rugged PVC coated polyester for durability.
- One interior and one exterior pocket for quick access and organization.
- Sturdy handle with box stitching for secure transportation and convenient hanging. Constructed of 1680d ballistic weave.
- Cat. Nos. 69406 and 69407 recommended for meters, testers, infrared guns and small tools.
- Cat. No. 69408 is recommended for meters, testers, borescopes, infrared guns and tools.







Cat. No.	Pockets	Width	Height	Depth	Weight
69406	1	4.50" (114 mm)	9.25" (235 mm)	2.25" (57 mm)	0.38 lbs. (0.17 kg)
69407	2	6.00" (152 mm)	10.25" (260 mm)	2.25" (57 mm)	0.53 lbs. (0.24 kg)
69408	2	7.00" (178 mm)	10.25" (260 mm)	2.25" (57 mm)	0.66 lbs. (0.30 kg)







### Features:

Constructed of double layered 1000 denier Cordura<sup>®</sup> Nylon.

Double nylon-stitched and rivet

reinforced for extra durability.



to abrasion, punctures, and tearing.

No break-in period; naturally forms and hugs the body, making it easy to wear for everyday use.

Heavy-duty, nylon webbing.

Washable.



Lightweight and comfortable in warm climates, soft and pliable in cold climates.

Oversized pockets and reinforced bottom for extra carrying capacity, as well as durability.

Cordura® is a registered trademark of INVISTA for durable fabrics.

### **Tool Pouches**

Cat. No.

5700

5701

5702

5703

5718

5719





Weight (lbs.)

.83

.64

.75

.74

.87







Cordura<sup>®</sup> is a registered trademark of INVISTA for durable fabrics.

Pockets (Total Number)

8

2

3

8

Overall Size

11" x 12" (279 mm x 305 mm)

5718

193

# **PowerLine™ Series**

### **Closeable Pouch**

### Additional Feature:

 Closeable pouch helps protect supplies and tools.



Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5714	tunnel	up to 2-1/4" (57 mm)	7-1/2" x 6-3/4" (190 mm x 171 mm)	.24

### **Tape Measure Holder**

### Additional Features:

- Holds most tape measures with belt clips.
- Stainless steel clip holder accepts most tape clips up to 1-3/4" wide.



5707

Cat. No.	<b>Belt Connection</b>	Belt Width	Overall Size	Weight (lbs.)
5707	tunnel	up to 2-1/4" (57 mm)	4-1/8" x 3-3/4" (104 mm x 95 mm)	.10

### **Tape Measure Pouch**

### Additional Features:

- Holds most 35-foot tape measures, fasteners, nails, or wire nuts.
- Two inside elastic loops fit screwdrivers, pencils, markers, etc.



5712

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5712	tunnel	up to 2-1/4" (57 mm)	8-1/4" x 4-1/2" (210 x 114 mm)	.24

### **Utility Knife Holder**

### Additional Feature:

 Holds standard utility knife or other small tools.



5716

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5716	tunnel		7-3/4" x 2-1/2" (197 mm x 64 mm)	.15

### **Hammer Holder**

### Additional Feature:

 Heavy-metal hammer loop riveted for additional strength.



5706

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight (lbs.)
5706	tunnel	up to 2-1/4" (57 mm)	4-1/8" x 5" (105 mm x 127 mm)	.19

### **Multi-Purpose Holder**

### Additional Feature:

 Holds a flashlight, cellular phone. or electrical tester



5708

Cat. No.	Belt Connection	Belt Width	Overall Size	Weight(lbs.)
5708	tunnel	up to 2-1/4" (57 mm)	3-1/4" x 8-1/2" (83 mm x 216 mm)	.13

### **Flashlight Holder**

### Additional Feature:

- Accommodates most "D" cell size battery flashlights up to 1-7/8" in diameter.
- Heavy-duty, 1-1/2" wide nylon webbing for extra strength.



5713

Cat. No.	<b>Belt Connection</b>	Belt Width	Overall Size	Weight (lbs.)
5713	tunnel	up to 2-1/4" (57 mm)	4-1/4" x 2-3/8" (108 mm x 60 mm)	.06

### **Adjustable Web Work Belt**

### Additional Feature:

- Heavy-duty, 2" wide nylon webbing for extra strength.
- Accommodates tunnel loop and slotted tool pouches and holders.
- Rugged metal buckle for quick release and adjustment.



**AWARNING:** This is NOT an occupational protective belt. NOT for fall arrest or back support

Cat. No.	Size	Width	Weight (lbs.)
5705	one size fits up to 54" waist	2" (51 mm)	.56

### **Padded Tool Belts**

### Additional Features:

- 5" cushioned pad for stability and comfort.
- Tapered front for comfort while bending.
- Heavy-duty 2" wide nylon web belt with rugged metal buckle.



Cat. No.	Size	Weight (lbs.)
5717	one size fits most	.84

Velcro® is a registered trademark of Velcro Industries B.V.

### **Padded Suspenders**

### Additional Features:

- Fully adjustable length front & back.
- Heavy-duty, 1-1/2" wide nylon web strap for extra strength and long wear.
- Convenient fastening system features genuine VELCRO® brand touch fasteners.
- Heavy-duty padding for user comfort.



5704L

Cat. No.	Size	Width	Weight (lbs.)
5704M	32" - 36" (813 mm - 914 mm)	2" (51 mm)	.95
5704L	36" - 40" (914 mm - 1016 mm)	2" (51 mm)	1.00
5704XL	40" – 44" (1016 mm – 1118 mm)	2" (51 mm)	1.05

### **4-Piece Combo Sets**

### Set consists of the following pieces:

- 8-Pocket Tool Pouch (Cat. No. 5701).
- 3-Pocket Utility Pouch (Cat. No. 5703).
- Hammer Holder (Cat. No. 5706).
- Padded Tool Belt (Cat. No. 5704).



Cat. No.	Size	Width of Belt	Weight (lbs.)
5709M	32" - 36" (813 mm - 914 mm)	2" (51 mm)	2.71
5709L	36" - 40" (914 mm - 1016 mm)	2" (51 mm)	2.77
5709XL	40" – 44" (1016 mm – 1118 mm)	2" (51 mm)	2.80

### **4-Piece Electrician's Combo Sets**



- 19-Pocket Tool Pouch (Cat. No. 5719).
- Hammer Holder (Cat. No. 5706).
- Padded Tool Belt (Cat. No. 5704).



5710M

Cat. No.	Size	Width of Belt	Weight (lbs.)
5710M	32" - 36" (813 mm - 914 mm)	2" (51 mm)	2.75
5710L	36" - 40" (914 mm - 1016 mm)	2" (51 mm)	2.80
5710XL	40" – 44" (1016 mm – 1118 mm)	2" (51 mm)	3.05

All dimensions are in inches and (millimeters)

**AWARNING:** This is NOT an occupational protective belt.

AWARNING: NOT for fall arrest or back support.

# **Tool Belts**

### **Lightweight Tool Belt**

- Leather construction.
- Designed to carry lightweight tool pouches.

Cat. No.	Size	Width	Weight (lbs.)
5201	33" – 45" (838 mm – 1143 mm)	1" (25 mm)	.30



### **General-Purpose Belts**

- Strong, heavy-duty leather.
- · Removable single-tongue buckle held by two heavy-duty snaps.

Cat. No.	Size	Width	Weight (lbs.)
5202M	32" - 40" (813 mm - 1016 mm)	1-1/2" (38 mm)	.40
5202L	38" - 46" (965 mm - 1168 mm)	1-1/2" (38 mm)	.45
5202XL	46" – 54" (1168 mm – 1372 mm)	1-1/2" (38 mm)	.50



### **Lightweight Utility Belt**

- Strong, lightweight polypropylene web.
- Quickly adjusts for waist sizes through 52" (1321 mm).
- Accepts tunnel-loop and slotted pouches and holders.
- Tough, molded, non-metallic, slide-action buckle provides single-handed, quick release and adjustment.

Cat. No.	Color	Size	Width	Weight (lbs.)
5204	blue	one size fits all	2" (51 mm)	.20





### **Adjustable Web Tool Belt**

- Fits waist sizes up to 48".
- Accommodates tunnel loop and slotted tool pouches and holders.
- 2" wide polypropylene webbing.
- · Rugged metal buckle for quick release and easy adjustment.
- Corrosion resistant hardware.

Cat. No.	Size	Width	Weight (lbs.)
5225	48" (1219 mm)	2" (51 mm)	.60



### **Heavy-Duty Embossed Tool Belts**

- Strong, heavy-duty rigging-leather.
- Equipped with a double-tongue buckle.

Cat. No.	Size	Width	Weight (lbs.)
5415S	32" - 40" (813 mm - 1016 mm)	2" (51 mm)	.63
5415	36" - 44" (914 mm - 1118 mm)	2" (51 mm)	.64
5415L	40" - 48" (1016 mm - 1219 mm)	2" (51 mm)	.64
5415XL	44" – 52" (1118 mm – 1321 mm)	2" (51 mm)	.65



All dimensions are in inches and (millimeters).

**AWARNING:** This is NOT an occupational protective belt.

**AWARNING:** NOT for fall arrest or back support.

### **Tool Belts**

# Cotton/Polyester Blend Tool Belt w/Quick-Release Buckle

- NOT an occupational protective belt. ONLY use as a tool belt.
- Features a forged, quick-release buckle for emergency situations where the user has to quickly disengage the belt (for example, when working over water or in grain elevators).
- Must be worn over the user's harness and clothing so it will drop free when released.
- Belt is made of a mildew-resistant blend of cotton/polyester webbing for comfort and strength.

Cat. No.	Size	Weight (lbs.)
5425M	30" - 44" (762 mm -1118 mm)	1.53
5425XL	38" - 58" (965 mm - 1473 mm)	1.67




### **Designed for Quick Release**

 Pull free end of release strap to disengage other end from retainer.

Pulling action rotates
r. clasp to open position.

3. Disengaged clasp allows belt to separate.







# **Ironworker's Heavy-Duty Tie-Wire Belts**

### Ironworker's Heavy-Duty Tie-Wire Belts

- Leather construction.
- Rugged 2" (51 mm) wide belt.
- Has separate reel-strap with its own buckle that lets you quickly and conveniently put on or take off a Klein tie-wire reel and optional pad without removing the belt or your tool pouch.
- Strong double-tongue buckle with keeper.
- Embossed basket-weave pattern.



Cat. No.	Waist Size	Belt Size Range	Width	Weight (lbs.)
5420S	36" (914 mm)	32" - 40" (813 mm - 1016 mm)	2" (51 mm)	.85
5420	40" (1016 mm)	36" - 44" (914 mm - 1118 mm)	2" (51 mm)	.95
5420L	44" (1118 mm)	40" - 48" (1016 mm - 1219 mm)	2" (51 mm)	1.05
5420XL	48" (1219 mm)	44" - 52" (1118 mm - 1321 mm)	2" (51 mm)	1.15

Tie-wire reel and tie-wire pad also available.

### Sets

### 10 Pocket Tool Pouch and Belt Set

- Combines the popular Cat. No. 5165, leather 10 pocket pouch, and Cat. No. 5202, general purpose leather belt, into one item.
- Belt is embossed to guide cutting and reduce size from large to medium.
- Belt fits 32" to 46" waist sizes (813 mm 1,168 mm) and is 1-1/2" (38 mm) wide.
- Four large capacity utility pockets, two pliers pockets, four screwdriver loops and knife snap.
- Pouch is riveted and stitched to assure long life.
- Top grain leather construction.

Cat. No.	Belt Width	Overall Size	Pockets	Size	Specialty Add-Ons	Weight (lbs.)
55210	1-1/2" (38 mm)	10" x 10" (254 mm x 254 mm)	10	32" - 46" (813 mm - 1168 mm)	knife snap	1.2



55210

All dimensions are in inches and (millimeters).

**AWARNING:** This is NOT an occupational protective belt.

**AWARNING:** NOT for fall arrest or back support.



### Suspenders

### Suspenders

- Clips and slides are nickel-plated for corrosion resistance.
- Extra-strong belt clips have alligator teeth for added gripping power.
- One size fits all.

Cat. No.	Color	Strap Width	Leather-Back Strap Spreader	Weight (lbs.)	
Nylon-We	b Susper	nders			
60210B	blue	2" (51 mm)	adjustable	.63	
Elastic-Back Suspenders					
60223B	blue	2" (51 mm)	non-adjustable	.60	



# **Suspender Accessories**


### **Leather Cushion Belt Pads**

- Deluxe leather pad is 4" (102 mm) wide.
- Thick leather back with four snap-open straps for easy attachment to any belt up to 2" (51 mm) wide.
- Sponge-padded leather liner has rounded edges, and is permanently stitched to the back.
- The most durable, most comfortable pad to wear, especially for prolonged work periods.
- When sizing a belt to accommodate this pad, add 2" to 4" to the belt waist size.

Cat. No.	Length	Width	Weight (lbs.)
87904	22" (559 mm)	4" (102 mm)	.99
87906	30" (762 mm)	4" (102 mm)	1.04



All dimensions are in inches and (millimeters).












### Tradesman Pro™ Organizer - Rolling Tool Bag

- Rugged 6-Inch wheels easily handle rough terrain.
- Load tested up to 200 lbs.
- Top has reinforced metal frame that stays open for easy loading/unloading.
- Heavy-duty telescoping handle.
- Withstands cold conditions.
- Orange interior for easy tool visibility.

Cat. No.	Length	Width	Height	Pockets	Weight
55452RTB	19" (483 mm)	12-1/2" (318 mm)	14" (356 mm)	24	19 lbs. (8.62 kg)







Wide open interior to accommodate large tools.

### Tradesman Pro™ Organizer – Hacksaw Electrician's Bag

- Fits standard hacksaws up to 16.5".
- Tough, durable molded bottom can withstand cold conditions.
- 1680D ballistic weave for durability.
- Orange interior for easy tool visibility.

Cat. No.	Length	Width	Height	Pockets	Weight
55453HSB	17-3/4" (451 mm)	13-1/2" (368 mm)	14-1/2" (368 mm)	48	8.15 lbs. (3.70 kg)



Top-loading hacksaw pocket with protective plastic lining.

### Tradesman Pro™ Organizer – Attachable Hacksaw Holder

- Quick link for attaching to tool bags.
- Fits standard hacksaws up to 16.5".
- Protective plastic lined interior.
- Top-loading for easy access to hacksaw.
- · Web strap with snap closure keeps hacksaw secure.
- 1680D ballistic weave for durability.







54453HSB








### **Tradesman Pro™ Organizer – Tech Backpack**

- Storage for adapters and cables.
- Organizer pocket for pens, phone, cables, and more.
- 25 pockets for tons of tool storage.
- Tough, durable molded bottom protects from the elements.
- Hard, molded front pocket protects safety glasses.
- 1680D ballistic weave for durability.

Cat. No.	Length	Width	Height		Exterior Pockets	Weight
55456BPL	14" (355.6 mm)	7" (177.8 mm)	18" (457.2 mm)	34	5	5.34 (lbs.) 2.42 (kg)







Orange interior to find tools faster.








### **Tradesman Pro™ Organizer – Tech Bag**

- Inside pocket for adapters and cables.
- Zipper pocket for files and paperwork.
- 22 pockets for plenty of tool storage.
- Rubber feet and water resistant material on bottom protects from the elements.
- 1680D ballistic weave for durability.
- Shoulder strap and handles for easy carrying.

Cat. No.	Length	Width	Height	Interior Pockets	Exterior Pockets	Weight
55455M	19" (444.5 mm)	6.5" (254 mm)	16" (355.6 mm)	2	53	8.92 (lbs.) 4.04 (kg)



Separate compartment keeps laptop protected from other tools.



Orange interior to find tools faster.



### Tradesman Pro™ Organizer – Electrician's Backpack

- 39 pockets for tons of tool storage.
- Orange interior for easy tool visibility.
- Wide opening fits power drills, meters, flashlights, etc.
- Tough, durable bottom protects from the elements.
- Large front pocket easily fits cables and tools.
- 1680D ballistic weave for durability.

Cat. No.	Length	Width	Height		Exterior Pockets	Weight
55421-BP	14" (355.6 mm)	7" (177.8 mm)	18" (457.2 mm)	34	5	5.34 (lbs.) 2.42 (kg)



Large front pocket easily fits fish tapes or tools and cables.



### Tradesman Pro™ Organizer – Ultimate Electrician's Bag

- 55 pockets for ultimate tool organization.
- Orange interior for easy tool visibility.
- Wide opening fits power drills, meters, laptops, etc.
- Tough, durable molded bottom protects from the elements.
- 1680D ballistic weave for durability.
- Shoulder strap and handles for easy carrying.



Cat. No.	Length	Width	Height		Exterior Pockets	Weight
55418-19	19" (444.5 mm)	6.5" (254 mm)	16" (355.6 mm)	53	2	8.92 (lbs.) 4.04 (kg)

### Tradesman Pro™ Organizer – Extreme Electrician's Bag

- 78 pockets for extreme tool storage.
- Orange interior for easy tool visibility.
- Wide center with removable pockets for easy access to tools.
- Tough, durable molded bottom protects from the elements.
- 1680D ballistic weave for durability.
- Shoulder strap and handles for easy carrying.

Cat. No.	Length	Width	Height	Interior Pockets	Exterior Pockets	Weight
55417-18	17.5" (482.6 mm)	10" (165.1 mm)	14" (406.4 mm)	53	25	9.51 (lbs.) 4.31 (kg)







### Tradesman Pro™ Organizer - Shoulder Pouch

- 16 pockets for better tool storage.
- Orange interior for easy tool visibility.
- Tough, durable rubber feet protect from the elements.
- 1680D ballistic weave for durability.
- Shoulder strap and handle for easy carrying.

Cat. No.	Length	Width	Height	Interior Pockets	Exterior Pockets	Weight
55419-SP	8" (203.2 mm)	5" (127 mm)	10" (254 mm)	9	7	2.2 (lbs.) 1 (kg)



Rubber feet protect the bottom surface from the elements.

55419-SP

### Tradesman Pro™ Organizer - 8-Inch Tote

- 20 pockets for greater tool storage.
- Orange interior for easy tool visibility.
- Removable zipper bag designed to fit compartment underneath.
- Tough, durable feet protect from the elements.
- 1680D ballistic weave for durability.
- Handle for easy carrying.

Cat. No.	Length	Width	Height	Interior Pockets	Exterior Pockets	Weight
55415-8	8" (203.2 mm)	8" (203.2 mm)	17" (431.8 mm)	9	11	4.77 (lbs.) 2.16 (kg)



Removable zipper bag designed to fit compartment underneath.



- 40 pockets for maximum tool storage.
- Orange interior for easy tool visibility.
- Removable zipper bag designed to fit compartment underneath.
- Tough, durable feet protect from the elements.
- 1680D ballistic weave for durability.
- Shoulder strap and handles for easy carrying.

Cat. No.	Length	Width	Height	Interior Pockets	Exterior Pockets	Weight
55416-10	10" (254 mm)	10" (254 mm)	12" (304.8 mm)	18	22	5.16 (lbs.) 2.34 (kg)



Removable zipper bag designed to fit compartment underneath.



55415-8





### **Canvas Tool Bags**

- Heavy-duty No. 8 natural canvas.
- Rivet-reinforced for durability.
- Steel-frame mouth with hinge for rugged use.
- Stitched and riveted leather handles for comfort and strength.
- Two retaining straps with buckles provide secure closure.
- Bottom and lower sides are covered with moisture-resistant vinyl.
- Non-scratch studs on base protect against wear.
- Shoulder strap kit available (Cat. No. 5102S).

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5102-12	12" (305 mm)	6" (152 mm)	10" (254 mm)	2.14
5102-14	14" (356 mm)	6" (152 mm)	14" (356 mm)	2.55
5102-16	16" (406 mm)	6" (152 mm)	14" (356 mm)	3.05
5102-18	18" (457 mm)	6" (152 mm)	14" (356 mm)	2.84
5102-20	20" (508 mm)	6" (152 mm)	15" (381 mm)	3.16
5102-22	22" (559 mm)	6" (152 mm)	15" (381 mm)	3.48
5102-24	24" (610 mm)	6" (152 mm)	15" (381 mm)	4.10



### **Deluxe Canvas Tool Bags**

- Multiple interior pockets for organization.
- Detachable shoulder strap can be adjusted for a perfect fit.
- Made of heavy-duty No. 8 natural canvas.
- Moisture-resistant vinyl bottom with non-scratch studs on the base to protect against wear.
- Steel frame mouth with hinge for rugged use.
- Stitched and riveted leather handles for long life.

Cat. No.	Length	Width	Height/Depth	Pockets	Weight (lbs.)
5102-14SP	12" (305 mm)	6" (152 mm)	10" (254 mm)	10	2.14
5102-16SP	14" (356 mm)	6" (152 mm)	14" (356 mm)	13	2.55
5102-18SP	16" (406 mm)	6" (152 mm)	14" (356 mm)	13	3.05
5102-24SP	18" (457 mm)	6" (152 mm)	15" (381 mm)	17	2.84





### **High-Bottom Canvas Tool Bags**

- Heavy-duty No. 8 natural canvas.
- Bottom and 8" (203 mm) of lower sides are covered with moisture-resistant vinyl.
- Non-scratch studs on base protect against wear.
- Steel-frame mouth with hinge for rugged use.
- Harness-leather handles with two retaining straps and buckles.
- Retro-fit bags with shoulder strap kit (Cat. No. 5102S). Kit includes leather strap with pad and snap hooks, rings and fasteners for attaching rings to bags.

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5105-20	20" (508 mm)	6" (152 mm)	15" (381 mm)	3.55
5105-24	24" (610 mm)	6" (152 mm)	15" (381 mm)	4.00





### Canvas Tool Bags - Multiple Pockets, Leather Bottom

- Steel-frame mouth with hinge for rugged use.
- Internal pockets in a variety of sizes.
- External pocket for additional carrying needs.
- Constructed of strong No. 8 natural canvas.
- Reinforced bottom supports heavy tools, blocks moisture, and provides durability at wear points.
- · Wide opening provides easy access to large tools.
- Bottom is protected from the elements by 6 studs.
- Includes: Shoulder strap mounts, (optional shoulder strap available, Cat. No. 58889) external pocket, leather bottom and 3" (76 mm) of sides covered with black leather, 2" (51 mm) wide web handles, leather handle wrap, and external tool loop handle in the webbing.



5003-18

Cat. No.	Length	Width	Height/Depth	Interior Pockets	Exterior Pockets	Retaining Straps	Weight (lbs.)
5003-18	18" (457 mm)	6" (152 mm)	14" (356 mm)	10	1	1	4.14
5003-20	20" (508 mm)	6" (152 mm)	15" (381 mm)	14	1	2	4.38

### **Cordura® Ballistic Nylon Tool Bag**

- Cordura<sup>®</sup> ballistic nylon, a high-performance fabric resistant to abrasions, tears and scuffs.
- Molded bottom made with a durable, impact modified polypropylene.
- Eight interior and two exterior pockets hold a wide assortment of hand tools and supplies.
- Large opening with reinforced steel frame maintains the bag's shape while loading and unloading.
- Heavy-duty nylon zipper closure and a large leather zipper-pull assure easy operation.
- Box-stitched 2" (51 mm) wide polypropylene padded carrying handles with comfortable leather wrap.
- Optional padded, slip-resistant adjustable shoulder strap (Catalog No. 58889) for hands-free mobility is available.

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5200-15	15" (381 mm)	8" (203 mm)	14-1/2 (368 mm)	3.59

Cordura® is a registered trademark of INVISTA for durable fabrics.



5200-15

### **Canvas Tool Bags**

- Heavy-duty No. 6 natural canvas.
- Double-layer canvas bottom.
- Reinforced, riveted web handles.

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5155	17" (432 mm)	9" (229 mm)	12" (305 mm)	1.56
5156	19" (483 mm)	9" (229 mm)	15" (381 mm)	1.82



### **Vinyl Equipment Bags**

- · Wide bag opening easily accommodates helmets and other equipment.
- Two large, outside pockets with Velcro® fastening (Cat. No. 5182BLA).
- Durable, double-stitched plastic bottom.
- · Webbing extends down side of bag from handles and shoulder strap for extra support & durability.
- Right-sized rain flap with Velcro<sup>®</sup> fastening.
- Adjustable, padded shoulder strap included.







Cat. No.	Exterior Pockets	Shoulder Strap	Color	Length	Height	Width	Weight (lbs)
5182BLA	2	Yes	black	24" (610 mm)	20" (508 mm)	10" (254 mm)	7.00
51810RA	1	Yes	orange	24" (610 mm)	20" (508 mm)	10" (254 mm)	7.00

### **Lineman Backpack**

- · Wide opening easily accommodates helmets, belts, and other equipment.
- Large front pocket for separate storage of gaffs, rubber gloves or other equipment.
- Durable, doulbe stiched plastic bottom with drain holes.
- Rain flap for top of pack.
- · Adjustable padded shoulder straps with adjustable waist strap.
- Padded back area.

Cat. No.	Length	Width	Height/ Depth	Interior Pockets	Exterior Pockets	Weight (lbs.)
51850RA	18" (457mm)	10" (254 mm)	23" (584 mm)	1	3	5.80



51850RA

### **Extra-Large Vinyl Equipment Bag**

- Orange vinyl-coated polyester fabric bag.
- Bottom extends 3" (76 mm) up the sides.
- Bottom of bag is protected by metal studs.
- Bottom reinforced with 1/4" (6 mm) plywood.
- Nylon-web handles extend around bag for extra support.
- Wide opening steel frame is securely riveted in top of bag.
- Extra flap for storm protection.



Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5180	24" (610 mm)	10" (254 mm)	18" (457 mm)	6.00









### **Tool Totes**™

- Onstructed of rugged, 600 x 300 denier polyester to resist wear and tear on the jobsite.
- 2" wide (51 mm), polypropylene padded carrying handles with comfortable leather wrap.
- Water-resistant to avoid the build-up of mold and mildew.
- Exterior pockets hold a variety of tools and a mobile phone.
- Multiple interior pockets and a large interior compartment for a wide assortment of tools and supplies (only with Cat. No. 58888 and Cat. No. 58890).
- Durable molded bottom with drain holes to prevent water retention.
- Contoured, padded, slip-resistant shoulder strap for hands-free mobility (included with 58888 and 58890).
- Heavy-duty chain tape thong (58890 only).



Cat. No	Interior Pockets	Exterior Pockets	Chain Tape Thong	Shoulder Strap (Cat. No. 58889)	Length	Width	Height/Depth	Weight (lbs.)
58886	-	7	No	No*	15-1/2" (394 mm)	7-1/2" (191 mm)	10" (254 mm)	2.42
58888	5	7	No	Yes	15-1/2" (394 mm)	7-1/2" (191 mm)	10" (254 mm)	3.01
58890	7	10	Yes	Yes	15-1/2" (394 mm)	7-1/2" (191 mm)	10" (254 mm)	3.41

<sup>\*</sup>Optional shoulder strap (Cat. No. 58889) available.

### **Tool Organizer**

- Constructed of double-layered, 600 x 300 denier polyester to resist wear and tear on the jobsite.
- Water-resistant to avoid the buildup of mold and mildew.
- Double layer of polyester at bucket edges for durability.
- Interior pockets include: three tool sleeves, one power tool/cord sleeve, and six universal pockets.
- Exterior pockets include: nine screwdriver/nut driver pockets, eleven pliers pockets, eleven utility pockets, two wire stripper pockets, and two Velcro® closeable pockets.
- Heavy-duty webbing keeps pockets open for easy access to supplies and tools.

Cat. No.	Interior Pockets	Exterior Pockets	Nominal Size	Weight (lbs.)
5777	10	35	fits standard 5-gallon buckets	3.90

VELCRO® is a registered trademark of Velcro Industries B.V. Tools NOT included.



### **Ten-Compartment Drawstring Bag**

- 12-oz. olive canvas.
- Ten compartments to hold small parts.
- Drawstring for easy closing.

Cat. No.	Diameter	Height/Depth	Weight (lbs.)
5151	11" (279 mm)	6" (152 mm)	.41



### **Deluxe Leather Bags**

- Rugged tool bag made of extra-heavy leather.
- Removable, padded shoulder strap.
- Three-ply bottom with steel studs.
- Retaining straps extend around bag for extra support.

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5108-18	18" (457 mm)	7" (178 mm)	8" (203 mm)	4.77
5108-20	20" (508 mm)	7" (178 mm)	8" (203 mm)	5.17
5108-24	24" (610 mm)	7" (178 mm)	8" (203 mm)	5.50



### **Leather Tote Bag**

- Rugged tool bag made of extra-heavy leather.
- Stitched and riveted construction.
- Reinforced ends.
- Double-ply bottom with steel studs.

Cat. No.	Length	Width	Height/Depth	Weight (lbs.)
5115	15" (381 mm)	6-1/2" (165 mm)	7" (178 mm)	2.20



### **Contractor's Zipper Portfolios**

- Great for transporting contracts, quotations, work orders, plans, and schedules.
- Holds clipboards, binders, and mobile phones.
- Convenient storage for pliers, wrenches, screwdrivers, nut drivers, other tools and spare parts.
- · Heavy-duty zipper.
- Overall size: 17" (432mm) long x 12" (305mm) high.

Cat No.	Material	Color	Zipper	Weight (lbs.)
5136	Top Grain Leather	brown	brass	.84
5236	Cordura <sup>®</sup> Ballistic Nylon	black	nylon	.51
5336	No. 10 Canvas	natural	brass	.40

Cordura® is a registered trademark of INVISTA for durable fabrics.



### Zipper Bag - Top-Grain Leather

- Brushed cowhide leather with heavy-duty brass zipper.
- Convenient storage for pliers, wrenches, screwdrivers, nut drivers, other tools, and spare parts.

Cat. No.	Length	Height	Weight (lbs.)
5139L	12-1/2" (318 mm)	7" (178 mm)	.23







### **Zipper Bags**







- Constructed of No. 10 canvas with heavy-duty brass zipper (Cat. No. 5139).
- Convenient storage for pliers, wrenches, screwdrivers, nut drivers, other tools, and spare parts.
- Constructed of Cordura<sup>®</sup> ballistic nylon, a high-performance fabric resistant to abrasions, tears, and scuffs (Cat. Nos. 5139B, 5139C).
- Heavy-duty nylon zipper. (Cat. Nos. 5139B, 5139).
- Features the jungle stalker digitized camouflage pattern for maximum concealment (Cat. Nos. 5139C).
- Heavy-duty nylon stitching and zipper ensure durability and long life (Cat. Nos. 5139C).

Cat. No.	Material	Length	Height	Weight (lbs.)
5139	canvas	12-1/2" (318 mm)	7" (178 mm)	.19
5139B	Cordura® Ballistic Nylon	12-1/2" (318 mm)	7" (178 mm)	.24
5139C	Cordura® Camouflage	12-1/2" (318 mm)	7" (178 mm)	.14
5139L	Leather	12-1/2" (318 mm)	7" (178 mm)	.23

Cordura® is a registered trademark of INVISTA for durable fabrics.

### **Padded Cordura® Zipper Bag**

- Constructed of Cordura®, a high performance fabric resistant to abrasions, tears, and scuffs.
- Three-layer padding provides additional protection to contents.
- Heavy-duty nylon zipper.
- Overall size: 12-1/2" (318 mm) x 7" (178 mm).

Cat. No.	Material	Length	Height	Color	Weight (lbs.)
5139PAD	Cordura <sup>®</sup> Ballistic Nylon	12 -1/2" (318 mm)	7" (178 mm)	black	.28



Cordura<sup>®</sup> is a registered trademark of INVISTA for durable fabrics.

5139PAD

### Zipper Bags - Canvas, 4-Pack

- Includes four assorted colors to organize and categorize important tools.
- Constructed of No. 10 canvas with heavy-duty brass zipper.





Cat No.	Description	Weight (lbs.)
5140	4 zipper bags - olive, orange, royal blue, yellow	.80
5141	4 zipper bags - brown, black, gray, red	.80

- Convenient storage for pliers, wrenches, screwdrivers, nut drivers, other tools and spare parts.
- Overall size: 12-1/2" (318 mm) long x 7" (178 mm) high.

### Canvas Zipper Bags – Consumables

- Constructed of No. 8 canvas, with heavy-duty brass zipper.
- Convenient storage for wire nuts, connectors and other consumables.
- 3-1/2" wide bottom for stability when standing; easy access when open.
- Brass grommet for hanging or attaching to belt or clip.
- Overall size: 10" (254 mm) long x 8" (203 mm) tall x 3-1/2" (89 mm) wide.

Cat. No.	Material	Length	Height	Width	Color	Weight (lbs.)
5539RED	canvas	10" (254 mm)	8" (203 mm)	3- 1/2" (89 mm)	red	.25
5539BLU	canvas	10" (254 mm)	8" (203 mm)	3- 1/2" (89 mm)	blue	.25
5539YEL	canvas	10" (254 mm)	8" (203 mm)	3- 1/2" (89 mm)	yellow	.25
5539NAT	canvas	10" (254 mm)	8" (203 mm)	3- 1/2" (89 mm)	natural	.25
5539CPAK	canvas	see above	see above	see above	3-pack: red, blue, yellow	.75









5539RED



### Glove Bags — Canvas

- Made of durable canvas.
- Has an expansion gusset, 5-1/2" (140 mm) across the top and 2-3/4" (70 mm) at bottom.
- Brass grommets in bottom for ventilation.
- Supplied with two-way snap.
- Includes safety notice to remind workers of the importance of using gloves.

Cat. No.	Canvas	Length	Width	Top Depth	Bottom Depth	Weight (lbs.)
5121-15	No. 4	15" (381 mm)	8" (203 mm)	5-1/2" (140 mm)	2-3/4" (70 mm)	.74
5121-19	No. 4	19" (483 mm)	8" (203 mm)	5-1/2" (140 mm)	2-3/4" (70 mm)	.88
5124-15	No. 10	15" (381 mm)	8" (203 mm)	4" (100 mm)	4" (100 mm)	.60
5124-17	No. 10	17" (432 mm)	8" (203 mm)	4" (100 mm)	4" (100 mm)	.65
5124-19	No. 10	19" (483 mm)	8" (203 mm)	4" (100 mm)	4" (100 mm)	.70



5121-15

### **Combination Glove and Sleeve Bags**

- Panels are tough No. 4 canvas.
- Provides separate storage for gloves and sleeves.
- Brass grommets in bottom for ventilation.
- Bags are 8" (203 mm) wide.
- Supplied with two-way snap.
- Includes safety notice to remind workers of the importance of using gloves.

Cat. No.	Length	Width	Bottom Depth	Weight (lbs.)
5122-16	16" (406 mm)	8" (203 mm)	4-13/16" (122 mm)	.98
5122-18	18" (457 mm)	8" (203 mm)	4-13/16" (122 mm)	1.05



5122-16

# **Tool Bag Accessories**

### **Shoulder Strap Kit**

- Adjustable leather shoulder strap for Cat. Nos. 5102 and 5105 series canvas tool bags.
- Complete kit contains leather strap with pad and snap hooks, rings and fasteners for attaching rings to bags.



Cat. No.	Weight (lbs.)
5102S	.78

### **Padded Adjustable Shoulder Strap**

- Shoulder strap for Tool Tote<sup>TM</sup> and 5003 series canvas tool bags.
- Adjustable from both ends for a perfect fit.



Cat. No.	Weight (lbs.)
58889	.36





### **Metal Tool Box & Slide Racks**

### **Extra-Deep All-Purpose Tool Box**

- A popular choice for all-around use.
- Big-capacity box with the necessary strength and rigid construction.
- Heavy-duty three-compartment tote tray with big, easy-grip handle.
- Double drawbolts plus hasp and staple for padlocks up to 3/8" (10 mm) in diameter (padlock not included).
- Protective, red, baked-enamel finish.

Cat. No.	Length	Depth	Height	Weight (lbs.)
54401	20" (508 mm)	8" (196 mm)	9" (220 mm)	11.55







### **Slide Racks**

- · Holds Klein mid-size or extra-large storage boxes.
- Boxes not included with rack, must be ordered separately.
- Welded, extra-rigid, all-steel construction.
- Metallic-gray, baked-enamel finish.
- Boxes ride in and out on heavy-duty channel tracks that permit covers to open all the way for full access.
- Heavy tabs prevent boxes from being accidentally pulled out, yet allow boxes to be easily removed when desired.
- Locking bars can be readily attached to prevent unauthorized access.

Cat. No.	Holds	Length (Front to Back)	Width	Height	Weight (lbs.)
54474	4 Klein mid-size storage boxes	11-3/4" (298 mm)	15-1/4" (387 mm)	10-3/4" (273 mm)	20.30
54476	6 Klein mid-size storage boxes	11-3/4" (298 mm)	15-1/4" (387 mm)	16-3/8" (416 mm)	28.75
54477	4 Klein extra-large storage boxes	15-3/4" (400 mm)	20" (508 mm)	15" (381 mm)	37





### **Slide-Rack Locking Bars**

- Steel bars lock to secure mid-size storage boxes in slide racks.
- Front hasp pivots down to allow locking bar to open.
- Available for Klein four-box and six-box racks.
- Strong piano hinge.
- Metallic-grey baked-enamel finish.
- Mounting holes allow for easy installation with sheet metal screws or pop rivets.

Cat. No.	Description	Weight (lbs.)
54484	locking bar for Cat. No. 54474 slide rack	.25
54486	locking bar for Cat. Nos. 54476 & 54477 slide racks	.35



54484

### **Extra-Large Parts Storage Boxes & Slide Racks**

### **Extra-Large Compartment Boxes**

- Klein storage boxes are offered with a choice of compartment sizes and arrangements.
- Boxes feature strong, rigid, heavy-duty welded construction.
- Full-length piano hinged covers are designed to stay open for ease of access.
- Each box has a carrying handle, positive pull-down locking catch.
- Boxes have a heavy, metallic-gray baked-enamel finish.
- Box compartments feature high-impact styrene construction.
- Scoop-bottom design for easy parts removal and cleaning.
- Fits four-drawer extra-large slide rack Cat. No. 54477.



Cat. No.	Number of Compartments	Compartment Sizes	Length (Front to Back)	Width	Height	Weight (lbs.)
54445	16	4-3/8" x 2-7/8" (111 x 73 mm)	12" (305 mm)	18" (457 mm)	3" (76 mm)	7.55
54446	21	20 each 2-3/4" x 2-7/8" (70 x 73 mm) and one 3-3/4" x 11-7/8" (95 x 302 mm)	12" (305 mm)	18" (457 mm)	3" (76 mm)	7.60
54447	24	20 each 2-3/4" x 2-7/8" (70 x 73 mm) and four 3-3/4" x 2-7/8" (95 x 73 mm)	12" (305 mm)	18" (457 mm)	3" (76 mm)	7.95
54448	32	32 each 2-1/8" x 2-7/8" (54 x 73 mm)	12" (305 mm)	18" (457 mm)	3" (76 mm)	8.00

### **Adjustable-Compartment Parts Box**

- Movable dividers in this parts box allow compartment sections to be arranged and sized as desired.
- Three partitions, running from front to back, divide the box into four equal 4-1/2" x 12" (114 mm x 305 mm) sections.
- Nine straight metal dividers can be positioned anywhere between the partitions, in one-inch (25 mm) increments, to create the compartments desired.
- Boxes feature strong, rigid, heavy-duty welded construction.
- Full-length piano hinged covers are designed to stay open for ease of access.
- Each box has a carrying handle, positive pull-down locking catch.
- Boxes have a heavy, metallic-gray baked-enamel finish.
- Box compartments feature high-impact styrene construction.
- Scoop-bottom design for easy parts removal and cleaning.
- Fits four-drawer extra-large slide rack Cat. No. 54477.



Cat. No.	Description	Length (Front to Back)	Width	Height	Weight (lbs.)
54451	adjustable-compartment parts drawer with 3 fixed partitions and 9 movable dividers	12" (305 mm)	18" (457 mm)	3" (76 mm)	7.65







# Lineman Buckets & Accessories

Klein lineman buckets and accessories have been recognized for decades for their durability and dependability. They are built for strength to handle professional wear and tear.



\$

### **Canvas Buckets**

Rope handle reinforced with leather for water resistance and strength.

**Durable**, straight-wall and tapered-wall buckets are made of heavy-duty canvas.



The "No" refers to the canvas weight. No. 1 being the thickest and No. 10 being the thinnest.

> **High-density** polyethylene top ring for strength and chemical resistance.

### AWARNING:

- Inspect for damage before each use.
   Remove from service if bucket shows signs of wear.
  - Never exceed the working load limit.
- Completely close top before each use.



### **Leather-Bottom Buckets**

### Additional Features:

- Load Rated 100 lbs.
- No. 1 canvas.
- Leather reinforced bottom.
- Leather cuff extends 3" (76 mm) up the side.
- Inside pocket measures 8" x 8" (203 mm x 203 mm).
- Rope handle.

Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5104	12" (305 mm)	17" (432 mm)		2.71
5104S	12" (305 mm)	17" (432 mm)	swivel snap (Cat. No. 2012)	2.93
5104VT	12" (305 mm)	17" (432 mm)	VELCRO® closure	3.0

# 5104



### **Straight-Wall Buckets**

### Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.



Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5106	9" (229 mm)	14" (356 mm)	N/A	1.51
5106P	9" (229 mm)	14" (356 mm)	two 7" x 7" (178 mm x 178 mm) inside pockets	1.62
5106S	9" (229 mm)	14" (356 mm)	swivel snap (Cat. No. 2012)	1.80

### **Wide Opening Straight-Wall Buckets**

### Additional Features:

- Load Rated 75 lbs.
- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.



Cat. No.	Diameter	Height		Weight (lbs.)
5109	12" (305 mm)	15" (381 mm)	N/A	2.06
5109P	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket	2.12
5109S	12" (305 mm)	15" (381 mm)	swivel snap (Cat. No. 2012)	2.35
5109PS	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket and swivel snap (Cat. No. 2012)	2.40



## **Canvas Buckets**

#### **Vinyl Bucket Top**

- Top cover for canvas bucket designed to keep the elements out and tools securely inside.
- Compatible with Klein Tools 5104 and 5109 series buckets.
- Attaches with VELCRO®.
- Includes safety strap loop to ensure connection to bucket.
- Bucket not included.

Cat. No.	Diameter	Height	Weight (lbs)
51TOP	12.5" (318 mm)	3.5" (89 mm)	.4



51T0P

#### **Tapered-Wall Buckets**

#### Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.



Cat. No.	Top Diameter	Bottom Diameter	Height	Extra Features	Weight (lbs.)
5113	12" (305 mm)	9" (229 mm)	13" (330 mm)		1.55
5113S	12" (305 mm)	9" (229 mm)	13" (330 mm)	swivel snap (Cat. No. 2012)	1.84

#### Heavy-Duty Tapered-Wall Bucket

#### Additional Features:

- No. 4 canvas.
- Black molded polypropylene bottom.
- Rope handle.
- Riveted leather glove strap.
- Equipped with Cat. No. 2012 swivel snap hook.



Cat. No.	Top Diameter	Bottom Diameter	Height	Extra Features	Weight (lbs.)
5103S	12" (305 mm)	9" (229 mm)	12" (305 mm)	swivel snap (Cat. No. 2012)	1.95

#### **Heavy-Duty Tapered-Wall Buckets with Pockets**

#### Additional Features:

- No. 4 canvas.
- Black molded polypropylene bottom.
- Rope handle.
- Riveted leather glove strap.
- Equipped with Cat. No. 2012 swivel snap hook.

Cat. No.	Top Diameter	Bottom Diameter	Height	Outside Pockets	Extra Features	Weight (lbs.)
5171PS	12" (305 mm)	9" (229 mm)	12" (305 mm)	4 outside pockets	swivel snap (Cat. No. 2012)	2.20
5172PS	12" (305 mm)	9" (229 mm)	12" (305 mm)	15 inside pockets	swivel snap (Cat. No. 2012)	2.35





#### Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Sisal-rope handle.
- Tripod suspension rope for greater stability.
- Equipped with Cat. No. 2012 swivel snap hook.

Cat. No.	Length	Width	Height	Pockets	Extra Features	Weight (lbs.)
5144S	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets	swivel snap (Cat. No. 2012)	2.17
5152S	14" (356 mm)	7" (177 mm)	10" (254 mm)	26 inside pockets & 15 outside pockets	swivel snap (Cat. No. 2012)	2.46





5152S





#### AWARNING:

- Inspect for damage before each use.
- Remove from service if bucket shows signs of wear
- Never exceed the working load limit. · Completely close top before each use.

A strong reinforced web strap extends down the side of the bucket for extra weight capacity.

#### **Heavy Duty Top Closing Bucket**

- Load rated 150 lbs.
- Top of bucket zips closed.
- 14" diameter accommodates standard 5 gallon bucket.
- Body constructed of heavy-dutyNo. 1 canvas.
- Web strap extends down the side of the bucket.
- Leather reinforced bottom extends 3" up the side.
- Durable steel rim.



Holds 5 gallon bucket

Cat. No.	Diameter	Height	Weight
5104CLR17	14" (356 mm)	17" (439 mm)	6.70 lbs. (3.04 kg)
5104CLR22	14" (356 mm)	22" (559 mm)	6.95 lbs. (3.15 kg)

## **All Purpose Work Bucket**

- Load rated: 150 lbs.
- · Web strap extends downthe side of the bucket.
- Heavy duty plastic bottomwith drain holes.

Cat. No.	Diameter	Height	Weight
5109SLR	12" (305 mm)	15" (381 mm)	5.95 lbs. (2.70 kg)







5104CLR22

## **Canvas Buckets**

#### **Aerial-Basket Oval Bucket with 15 Interior Pockets**

#### Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Two nylon 66 polymer hooks (Cat. No. 5144H) included with Cat. No. 5144.

Cat. No.	Length	Width	Height	Pockets	Extra Features	Weight (lbs.)
5144	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets	two hooks (Cat. No. 5144H)	2.01
5144B	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets		1.5



#### **Hard Body Oval Buckets**

- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite (Cat. No. 5144BHB140S).
- Black molded polypropylene bottom with drain holes.
- Cat. No. 5144H hooks sold separately.









Kick Stand on back of Cat. No. 5144BHB

Cat. No.	Pockets	Handle	Color	Length	Height	Width	Weight (lbs)
5144BHB	14	No	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2
5144BHHB	14	Yes	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2
5144BHB140S	29	Yes	black	14" (356 mm)	10" (254 mm)	7" (178 mm)	3

## Hard Body Oval Bucket with Knife Sheath

- Includes leather skinning knife sheath and 14 other interior pockets.
- Orange, non-conductive plastic exterior maintains bucket shape.
- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite.
- Black molded polypropylene bottom with drain holes.
- Cat. No. 5144H hooks sold separately.



Knife Sheath inside of Cat. No. 5144HBS

Cat. No.	Interior Pockets	Handle	Color	Length	Height	Width	Weight (lbs)
5144HBS	15	Yes	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2



218

## **Canvas Buckets**

#### **Line-Hose Bag**

- No. 6 canvas with Cycolac top ring and molded bottom.
- Large enough to accommodate several pieces of hose.
- Can also be used to raise protective rubber blankets that are rolled.
- Leather cuff extends 3" (76 mm) up the side.
- Polypropylene rope handle is reinforced with leather.

Cat. No.	Diameter	Depth	Weight (lbs.)
5110-48	7" (178 mm)	48" (1219 mm)	1.91



5110-48

#### **Canvas Electrode Bag**

- Made of tough No. 4 canvas.
- Heat-resistant, hard leather bottom.
- Canvas loop for sliding over belt.



5471

Cat. No.	Diameter	Depth	Weight (lbs.)
5471	2-1/2" (64 mm)	15-1/2" (394 mm)	.25

#### **Canvas Tapered-Bottom Bag**

- No. 10 canvas.
- Two pockets are provided for small parts.
- Bottom is tapered so parts will stay in center.
- Equipped with a snap for hanging.



Cat. No.	Diameter	Depth	Weight (lbs.)
5143	6-1/2" (165 mm)	8" (203 mm)	.30



## **Aerial Aprons**

 Includes: ten hand tool pockets, two pouches, hammer loop and two drill bit holders (Cat. Nos. 51829, 51829M).

**Lineman Accessories** 

- Two pouches reinforced with heavy duty rivets.
- Cat. No. 5144H hooks sold separately.
- Hot stick pocket (Cat. No. 51829MHS).



Sewn-in magnet conveniently holds nuts, bolts and other small metal objects



Cat. No.	Interior Pockets	Magnet	Color	Width	Height	Weight (lbs.)
51829	18	No	orange	24" (609 mm)	23" (584 mm)	4
51829M	18	Yes	orange	24" (609 mm)	23" (584 mm)	4
51829MHS	16	Yes	orange	32" (813 mm)	27.5" (699 mm)	4

## Hooks

#### **Swivel Snap Hook**

#### Additional Features:

- This is NOT an occupational protective hook. NOT for human support.
- Bronze swivel snap hook made for use on canvas buckets.
- Maximum safe load is 150 lbs. (68 kg).

Cat. No.	Length	Width	Weight (lbs.)
2012	4-3/8" (111 mm)	1-5/8" (41 mm)	.28



#### **Hook for Aerial-Baskets**

- All weather, durable, nylon 66 polymer.
- Most manufacturers' aerial basket trucks accommodate bucket hook.
- Replacement hook for both Cat. No. 5144.

Cat. No.	Weight (lbs.)
5144H	.30



## Slings

#### **Pole Sling**

- For use where a running loop wrap around pole is desired.
- Nylon web stitched with nylon thread.
- NOT an occupational protective device. NOT for human support.

	<b>™NOT</b>	FOR HUMAN	SUPPORT	
 -				

5	6	0	(

Cat. No.	Rated Capacity (Maximum Working Load)		Overall Length	Width	Weight (lbs.)
	Choke Hitch	Basket Hitch			
5606	3000 lbs (1350 kg)	4700 lbs (2115 kg)	39" (991 mm)	2" (51 mm)	1.33

220

All dimensions are in inches and (millimeters).

**AWARNING:** This is NOT an occupational protective device. NOT for human support.





259

## **Block and Tackle**

- These are NOT occupational protective devices. NOT for human support.
- Sheaves are strong, yet are lightweight aluminum alloy with all-bronze bushings.
- · Light, galvanized-steel shell blocks are fitted with snubbing hooks to hold the load.
- Hooks fit under insulator and engage pin on cross arm.
- All Klein block and tackle use high-quality, 3/8" diameter rope.
- Available with standard snap hooks or guarded snap hooks (with snap hook nose lengthened to extend over the latch or keeper).
- Choice of forged hook Cat. No. 258 or swivel hook Cat. No. 259.
- Catalog numbers followed by S/R have rope spliced to block.
- Maximum safe load is 750 lbs. (338 kg).

#### **Anchor Hook**

- Forged hook is designed to fit under insulator and engage pin of cross arm.
- Maximum safe load 750 lbs. (340 kg).
- Standard on Klein block & tackle Cat. Nos. 1802-30 and H1802-30.

Cat. No.	Eye	Throat	Overall	Weight
	I.D.	Opening	Length	(lbs.)
258	5/8" (16 mm)	1-7/8" (48 mm)	5-1/2" (140 mm)	.42

#### **Swivel Anchor** Hook

- Swivel clevis on this forged hook will engage with snap on Klein block & tackle Cat. Nos. 1802-30 and H1802-30.
- Swivel prevents twisting and kinking of rope.
- Maximum safe load 750 lbs. (340 kg).

Cat. No.	Swivel	Throat	Overall	Weight
	Opening	Opening	Length	(lbs.)
259	1-3/16" x 1" (30 mm x 25 mm)	1-7/8" (48 mm)	6-1/2 " (165 mm)	.40

#### **Heavy-Duty Snap Hook**



- Snaps on with one hand.
- Forged hook may be used on many conventional steel blocks, 4" (102 mm) or smaller.
- Maximum safe load 8000 lbs. (3629 kg).

Cat. No.	Eye I.D.	Throat Opening	Overall Length	Weight (lbs.)
455	15/16" (24 mm)	1" (25 mm)	5" (127 mm)	.84

#### Rope

258

455



- Works with all block and tackle products.
- High-quality, 3/8" diameter rope.

Cat. No.	Diameter	Average Strength	Minimum Strength	Overall Length	Weight (lbs.)
48502	3/4" (9 mm)	3,600 (1600 kg)	3,200 (1500 kg)	25' (7,620 mm)	.78

#### **Blocks**

Made of light

Sheaves have



Cat. No.	Description	Weight (lbs.)
267	plain block	.76
H267	Cat. No. 267, but nose extends over keeper	.80
268	block with eye to splice line to block and rope tie-off	.91
H268	Cat. No. 268, but nose extends over keeper	1.00



**AWARNING:** These are NOT occupational protective devices. Do NOT use for human support.





## **Block and Tackle Packages**

# Block and Tackle with Standard Hooks



Component Part Number						
Cat. No.	267 Block	268 Block	258 Anchor Hook	259 Swivel Anchor Hook	Rope spliced to component number	Weight (lbs.)
1802-30	•	•	•			2.80
1802-30 S/R	•	•	•		268 Block	2.80
1802-30S	•	•		•		2.85
1802-30S S/R	•	•		•	268 Block	2.85







224

## **Block and Tackle Packages**

# Block and Tackle with Guarded Hooks





		Compo	nent Part Number			
Cat. No.	H267 Block	H268 Block	258 Anchor Hook	259 Swivel Anchor Hook	Rope spliced to component number	Weight (lbs.)
H1802-30	•	•	•			2.90
H1802-30 S/R	•	•	•		H268 Block	2.90
H1802-30 S	•	•		•		3.00
H1802-30S S/R	•	•		•	H268 Block	3.00



All dimensions are in inches and (millimeters).

**AWARNING:** These are NOT occupational protective devices. Do NOT use for human support.

# B



#### **Block and Tackle**

# Polypropylene Hand-Lines with Snap Hook



1804-60

- Made of 5/16" (8 mm) three-strand polypropylene rope spliced to eye of snap hook.
- Both lines 75' (23 m) long.
- Forged steel with swivel clevis and quick-acting plunger-style latch.

Cat. No.	Description	Weight (lbs.)
1803-60	75' (23 m) of 5/16" (8 mm) rope with Cat. No. 443A snap. Maximum safe load 250 lbs. (113 kg)	2.45
1804-60	75' (23 m) of 5/16" (8 mm) rope with Cat. No. 470 swivel snap. Maximum safe load 250 lbs. (113 kg)	2.20

#### **Howe Wire Tool**

- Strap is made of tough Klein-Kord<sup>®</sup>.
- Swivel hook is forged steel with large opening.
- Shank of hook is lengthened to reach under insulator.
- Other end has device to hold the load at any distance.
- All metal parts are galvanized.
- Max. safe load 500 lbs. (225 kg).



Cat. No.	Description	Weight (lbs.)
1702-20N	nylon strap 1" (25 mm) wide, 7' (2.1 m) long	1.95

#### **Snap Hook**

- General-purpose forged snap hook with eye at 90° to opening.
- Maximum safe load 1500 lbs. (675 kg).



s. (675 kg).

Cat. No.	Eye I.D.	Throat Opening	Overall Length	Weight (lbs.)
443A	1" (25 mm)	1/2" (13 mm)	5-1/2" (140 mm)	.52

#### Swivel Hook with Plunger Latch



470

KN1500P-EX

 Forged steel with swivel clevis and quick-acting plunger-style latch.

- Designed to take 1/2" (13 mm) or lighter hand lines.
- Swivel action prevents accidental fouling into secondary wires.
- Maximum safe load 750 lbs. (338 kg).

Cat. No.	Swivel	Throat	Overall	Weight
	Opening	Opening	Length	(lbs.)
470	1-3/16" x 1" (30 mm x 25 mm)	5/8" (16 mm)	5" (127 mm)	.30

## **Web Strap Ratchet Hoist** NEW • Large, non-conductive drum knob allows web slack to be adjusted with ease. 360° handle rotation. • 3/4 ton single line and 1-1/2 ton double line load rating. Tight ratcheting mechanism allows precise tensioning Meets ANSI/ASME B30.21-2005 & B30.10-2009 standards. Cat. No. **Pull Type** Approx. Weight Each Single/ Double 1.95 **Single Line Load Rating:** 1500 lbs. (675 kg) Min. to Max. Pulling Distance inches (mm): 20" - 138" (500 mm - 3500 mm) **Double Line**

All dimensions are in inches and (millimeters).

**AWARNING:** These are NOT occupational protective devices. Do NOT use for human support.

Min. to Max. Pulling Distance inches (mm):

Load Rating: 3000 lbs. (1350 kg)

26" - 79" (700 mm - 2000 mm)




## **Introduction to Wire Pulling Grips**

#### Quality

Trust the quality and reliability of Klein Grips. All authentic Klein Grips are manufactured, inspected and tested in the USA, in company owned plants by American workers. From the custom drop-forged quality steel to machining and heat treating, to pulling rated load and final inspection, Klein Grips are designed to help linemen get their jobs done.

#### Features:





Before leaving our manufacturing plant, each and every authentic Klein Grip is individually hand inspected and actuated for proper function. Grips are rigorously tested using the Magnuflux method and pulled to rated load to ensure the highest quality and reliability for which Klein Tools is known.

#### **Grip Recommendation**

Klein Tools offers a service of recommending the proper grip for a particular application based on a sample of cable. This service is free of charge. All that we require is a minimum 3' (about 1 meter) length of cable.

Klein Tools has been manufacturing grips for over 135 years. All Klein Grips are manufactured, and tested in the USA.

If there is ever a question about the safe condition of any grip, please contact Klein Tools Customer Service at 847.821.5500 or 800.553.4676.



#### **Recommended Care and Maintenance**

#### **Grip Cleaning, Lubricating and Inspecting**

The following guidelines have been established to keep all grips in good working condition.

#### **Cleaning**






■ Step 1. Use the Klein Grip Cleaning Wire Brush Set (Cat. No. 25450) or emery cloth to clean the surfaces of grip jaws (photo #1).



**Step 2.**Spray degreaser on the grip jaws, all joints and moving parts (photo #2).



■ Step 3. Use the Klein Grip Cleaning Wire Brush to remove dirt and debris from the grip jaws (photo #3).



**Step 4.** Wipe grips dry with soft cloth. Repeat all cleaning steps as necessary until grip is completely clean (photo #4).

#### Lubricating








◆ Step 5.

Apply lubricant to all joints and moving parts. Do NOT lubricate gripping surfaces of jaws (photos left #5).

**Step 6.** Carefully inspect jaw condition, proper alignment of jaws and all parts, and possible distortion caused by exceeding safe-load specifications. Grips should operate smoothly. Spring-loaded grips should lock open with loop handle in "Down" position and should close automatically with loop handle "Up." The Klein Parallel Jaw Grip may be tested by opening and closing the jaws by hand, exercising proper caution. All parts and rivets should be checked for distortion (illustration #6).



**Never repair any grip.** Grips that are bent, misaligned, or otherwise distorted should be discarded and replaced. If there is ever a question about the safe condition of any grip, please contact Klein Tools Customer Service directly at **847-821-5500** or **800-553-4676**.

**Note:** Conductors may have a die-grease coating which can deposit on grip jaws. New conductors should be wiped clean before grip application. Grip jaws should be wiped clean of all grease before use.





## **Types of Wire Pulling Grips**

Klein Chicago<sup>®</sup>, Parallel Jaw and Haven's<sup>®</sup> Grips are widely used in the power, communications, and general construction fields to pull wire and cable. The grips maintain temporary tension until the wire or cable can be permanently terminated.

#### **Klein Chicago® Grips**

Authentic Chicago Grips are designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand.

- Locking loop handles allow the jaws to be held in an open position for easy placement on wire or cable.
- Available in Round, Double V and Single V jaw contours.



#### **Parallel Jaw Grips**

Lightweight compact parallel jaw grips pull an exceptionally wide range of cable types and sizes.

- Latch helps maintain cable position.
- Large-diameter eye accommodates large hooks on hoists, winches and tackle blocks.
- Available in Round and Double V jaw contours.



#### Haven's® Grips

Haven's Grips are designed for use when a light, compact grip is desired where conductor deformation is not a factor.

- Knurled eccentric jaw applies gripping pressure to 1/4" of cable area.
- Some models include a swing latch that holds cable securely in jaw.
- · Recommended for messenger and guy strand and wire rope.
- 1625 Series can be used for wire rope.



#### **Hot-line Latch**

The hot-line latch is designed for placing a grip on cable with a hot-line stick. The three notches in the hot-line latch adjust the balance of the grip to better match the direction of the cable sag.

- When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire.
- Standard hot-line grips are not supplied with springs or lock-open features.



All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

AWARNING: Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.





230

## **Types of Jaw Contours**

d
-
-
ended for:
Wide Range of Cables Cat. No.
1613-40H, 1671-10 1672-10 1686-10 1686-20 1686
ended for:
Weatherproof and PVC Covered Copper Steel Strand Of Cables Cat. No. Cat. No. Cat. No.
THES ARES ARES ARES ARES ARES ARES ARES AR
ended for:
d
Wire Rope) or Wire Rope) (For Wire Rope)
Bee elli 1 (EF elli 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1

### **Selecting the Proper Grip**

Three basic factors are needed in order to determine the proper grip for each specific application:

- 1. Type of wire or cable (ACSR, ACSS, AAC, Copper, Steel Strand).
- 2. AWG or MCM (diameter) of wire or cable.
- 3. Maximum safe load required.

Klein Grips are organized according to these three factors to make it easy for you to choose the proper grip.





For Cable	Diameter			MAXIMUM SAFE LOAD			See facing page for grip details.
_	<b>636 MCM</b> 53" (6.35 mr	n - 24.21 ı	mm)	A	В	<b>C</b>	<b>D</b>
	-			4,500 lbs (2041 kg)	8,000 lbs (3629 kg)	15,000 lbs (6803 kg)	20,000 lbs (9072 kg)
AWG or MCM Cable Size	Diameter 1 inches (mm) S	No. of Alum. & Steel Strands	Code Word	Cat. No.	Cat. No.	Cat. No.	Cat. No.
4	.250" (6.35 mm)	6 x 1	Swan	1656-20, 1656-20H & S1656-20H			
2	.257" (6.53 mm) .316" (8.03 mm)	7 x 1 6 x 1	Swanate Sparrow	1656-20, 1656-20H & S1656-20H 1656-20, 1656-20H, S1656-20H,		1628-16PE*	
			эраном	1656-30, 1656-30H & S1656-30H			
2	.325" (8.26 mm)	7 x 1	Sparate	1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H & S1656-30H		1628-16PE*	
I	.354" (9.02 mm)	6 x 1	Robin	1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H & S1656-30H		1628-16PF*	
1/0	.398" (10.11 mm)	6 x 1	Raven	1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H		1628-16PG*	
2/0	.447" (11.35 mm)	6 x 1	Quail	1656-30, 1656-30H & S1656-30H		1628-16PG*	
3/0	.502" (12.75 mm)	6 x 1	Pigeon	1656-30, 1656-30H & S1656-30H		1628-16PH*	
4/0	.563" (14.30 mm)	6 x 1	Penguin		1656-40, 1656-40H & S1656-40H	1628-16PI*	
266.8 MCM	.609" (15.47 mm)	18 x 1	Waxwing		1656-40, 1656-40H & S1656-40H	1628-16PJ*	
266.8 MCM	.642" (16.31 mm)	26 x 7	Partridge		1656-40, 1656-40H & S1656-40H	1628-16PK*	
300 MCM	.680" (17.27 mm)	26 x 7	Ostrich		1656-40, 1656-40H & S1656-40H	1628-16PK*	
336.4 MCM	.684" (17.37 mm)	18 x 1	Merlin		1656-40, 1656-40H & S1656-40H	1628-16PK*	
336.4 MCM	.720" (18.31 mm)	26 x 7	Linnet		1656-40, 1656-40H & S1656-40H	1628-16PL*	
336.4 MCM	.741" (18.82 mm)	30 x 7	Oriole			1628-16PL*	
397.5 MCM	.743" (18.87 mm)	18 x 1	Chickadee		1656-50, 1656-50H & S1656-50H	1628-16PL*	
397.5 MCM	.772" (19.61 mm)	24 x 7	Brant		1656-50, 1656-50H & S1656-50H	1628-16PM*	
397.5 MCM	.783" (19.89 mm)	26 x 7	Ibis		1656-50, 1656-50H & S1656-50H	1628-16PM*	
397.5 MCM	.806" (20.47 mm)	30 x 7	Lark		1656-50, 1656-50H & S1656-50H	1628-16PM*	
477 MCM	.814" (20.68 mm)	18 x 1	Pelican		1656-50, 1656-50H & S1656-50H	1628-16PM*	
477 MCM	.846" (21.49 mm)	24 x 7	Flicker		1656-50, 1656-50H & S1656-50H	1628-16PN*	1628-30N*
477 MCM	.858" (21.79 mm)	26 x7	Hawk		1656-50, 1656-50H & S1656-50H	1628-16PN*	1628-30N*
556.5 MCM	.879" (22.33 mm)	18 x 1	Osprey		1656-60, 1656-60H & S1656-60H	1628-16PN*	1628-30N*
477 MCM	.883" (22.43 mm)	30 x 7	Hen		1656-60, 1656-60H & S1656-60H	1628-16PN*	1628-30N*
556.5 MCM	.914" (23.22 mm)	24 x 7	Parakeet		1656-60, 1656-60H and S1656-60H		1628-300*
556.5 MCM	.927" (23.55 mm)	26 x 7	Dove		1656-60, 1656-60H & S1656-60H		1628-300*
636 MCM	.940" (23.88 mm)	18 x 1	Kingbird		1656-60, 1656-60H & S1656-60H		1628-300*
556.5 MCM	.953" (24.21 mm)	30 x 7	Eagle		1656-60, 1656-60H & S1656-60H		1628-300*
605 MCM	.953" (24.21 mm)	24 x7	Peacock		1656-60, 1656-60H & S1656-60H		1628-300*

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

AWARNING: When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

AWARNING: Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

<sup>&</sup>quot;S" is for spring. "H" is for hot latch.
\*Special order only. Please allow 30 days for delivery. These are not returnable.

#### Chicago® Grip - 1656 Series

- Round, smooth inside jaw contour on this series of grips is ideal for bare ACSR.
- Smooth jawed grips with maximum contact are less likely to cause cable deformation.



#### A 4,500 lbs. (2,041 kg) Maximum Safe Load

Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable AWG	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1656-20	1656-20H	S1656-20H	4 - 1/0	.250"398" (6.35 mm - 10.11 mm)	4" (102 mm)	3 lbs. (1.36 kg)
1656-30	1656-30H	S1656-30H	2 - 3/0	.325"502" (8.25 mm - 12.75 mm)	4-3/4" (121 mm)	3.75 lbs. (1.70 kg)

#### 8,000 lbs. (3,629 kg) Maximum Safe Load

Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable AWG or MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1656-40	1656-40H	S1656-40H	4/0 - 336.4 MCM	.563"720" (14.30 mm - 18.29 mm)	5-1/2" (140 mm)	8.30 lbs. (3.76 kg)
1656-50	1656-50H	S1656-50H	397.5 MCM - 477 MCM	.743"858" (18.82 mm - 21.79 mm)	5-1/2" (140 mm)	8.30 lbs. (3.76 kg)
1656-60	1656-60H	S1656-60H	477 MCM - 636 MCM	.879"953" (22.33 mm - 24.21 mm)	5-1/2" (140 mm)	8.20 lbs (3.71 kg)

#### Chicago® Grip - 1628-16P and 1628-30 Series

- Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation.
- Designed for large-diameter ACSR cables.

#### 15,000 lbs. (6,803 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable AWG or MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-16PE*	2	.316"325" (8.03 mm - 8.25 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PF*	1	.354" (8.99 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PG*	1/0 - 2/0	.398"447" (10.11 mm - 11.35 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PH*‡	3/0	.502" (12.75 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PI*	4/0	.563" (14.30 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PJ*	266.8 MCM	.609" (15.47 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PK*	266.8 MCM - 336.4 MCM	.642"684" (16.31 mm - 17.37 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PL*	336.4 MCM - 397.5 MCM	.720"743" (18.29 mm - 18.87 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PM*	397.5 MCM - 477 MCM	.772"814" (19.61 mm - 20.68 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PN*	477 MCM - 556.5 MCM	.846"883" (21.49 mm - 22.43 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)

## D 20,000 lbs. (9,072 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-30N**	477 MCM - 556.5 MCM	.846"883" (21.49 mm - 22.43 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-300**	556.5 MCM - 636 MCM	.914"953" (23.22 mm - 24.21 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)





- \*These grips are special order only. Please allow 30 days for delivery. These are not returnable.
- $^{\star\star}\text{Maximum}$  safe stringing tension 12,500 lbs to minimize cable deformation.

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.







For Cable Diameter

See facing page for grip details.

605 - 2515 MCM .966" - 1.88" (24.54 mm - 47.75 mm)		<b>C</b> 20,000 lbs (9,072 kg)	<b>D</b> 25,000 lbs (11,340 kg)	E 25,000 lbs.		
MCM Cable Size	Diameter inches (mm)	No. of Alum. & Steel Strands	Code Word	Cat. No.	Cat. No.	(11,340 kg) Cat. No.
605 MCM	.966" (24.54 mm)	26 x 7	Squab	1628-30P*		1628-50P*
636 MCM	.977" (24.82 mm)	24 x 7	Rook	1628-30P*		1628-50P*
636 MCM	.991" (25.15 mm)	26 x 7	Grosbeak	1628-30P*		1628-50P*
605 MCM	.994" (25.25 mm)	30 x 19	Teal	1628-30P*		1628-50P*
605 MCM	.994" (25.25 mm)	30 x 7	Wood Duck	1628-30P*		1628-50P*
666.6 MCM	1.00" (25.40 mm)	24 x 7	Flamingo	1628-30P*		1628-50P*
666.6 MCM	1.014" (25.76 mm)	26 x 7	Gannet	1628-30P*		1628-50P*
636 MCM	1.019" (25.88 mm)	30 x 19	Egret	1628-30R*		1628-50R*
636 MCM	1.019" (25.88 mm)	30 x 7	Scoter	1628-30R*		1628-50R*
795 MCM	1.040" (26.41 mm)	36 x 1	Coot	1628-30R*		1628-50R*
715.5 MCM	1.051" (26.70 mm)	26 x 7	Starling	1628-30R*		1628-50R*
795 MCM	1.063" (27.00 mm)	45 x 7	Tern	1628-30R*		1628-50R*
715.5 MCM	1.081" (27.46 mm)	30 x 19	Redwing	1628-30S*		1628-50S*
795 MCM	1.092" (27.76 mm)	54 x 7	Condor	1628-30S*		1628-50S*
795 MCM	1.092" (27.74 mm)	24 x 7	Cuckoo	1628-30S*		1628-50S*
795 MCM	1.107" (28.14 mm)	26 x 7	Drake	1628-30S*		1628-50S*
900 MCM	1.131" (28.73 mm)	45 x 7	Ruddy	1628-30S*		1628-50S*
795 MCM	1.140" (28.96 mm)	30 x 19	Mallard	1628-30S*		1628-50S*
900 MCM	1.162" (29.51 mm)	54 x 7	Canary	1628-30T*		1628-50T*
954 MCM	1.165" (29.59 mm)	20 x 7	Corncrake	1628-30T*		1628-50T*
954 MCM	1.165" (29.59 mm)	45 x 7	Rail	1628-30T*		1628-50T*
954 MCM	1.175" (29.85 mm)	48 x 7	Towhee	1628-30T*		1628-50T*
954 MCM	1.196" (30.38 mm)	54 x 7	Cardinal	1628-30T*		1628-50T*
954 MCM	1.196" (30.38 mm)	24 x 7	Redbird	1628-30T*		1628-50T*
1033.5 MCM	1.212" (30.81 mm)	45 x 7	Ortolan	1628-30U*	1628-40U*	1628-50U*
1033.5 MCM	1.245" (31.65 mm)	54 x 7	Curlew	1628-30U*	1628-40U*	1628-50U*
1113 MCM	1.258" (31.95 mm)	45 x 7	Bluejay	1628-30U*	1628-40U*	1628-50U*
1113 MCM	1.292" (32.84 mm)	54 x 19	Finch		1628-40W*	1628-50W*
1192.5 MCM	1.302" (33.07 mm)	45 x 7	Bunting		1628-40W*	1628-50W*
1272 MCM	1.317" (33.45 mm)	36 x 1	Skylark		1628-40W*	1628-50W*
1192.5 MCM	1.337" (33.99 mm)	54 x 19	Grackle		1628-40X*	1628-50X*
1272 MCM	1.345" (34.16 mm)	45 x 7	Bittern		1628-40X*	1628-50X*
1272 MCM	1.381" (35.10 mm)	54 x 19	Pheasant		1628-40X*	1628-50X*
1351.5 MCM	1.386" (35.20 mm)	45 x 7	Dipper		1628-40X*	1628-50X*
1351.5 MCM	1.424" (36.17 mm)	54 x 19	Martin		1628-40Y*	1628-50Y*
1431 MCM	1.427" (36.25 mm)	45 x 7	Bobolink		1628-40Y*	1628-50Y*
1431 MCM	1.465" (37.21 mm)	54 x 19	Plover		1628-40Z*	1628-50Z*
1590 MCM	1.504" (38.15 mm)	45 x 7	Lapwing		1628-40Z*	1628-50Z*
1590 MCM	1.544" (39.24 mm)	54 x 19	Falcon		1628-40A*	1628-50A*
1780 MCM	1.602" (40.69 mm)	84 x 19	Chukar			1628-50B*
2034.5 MCM	1.681" (42.70 mm)	72 x 7	Mockingbird			1628-50C*
2167 MCM	1.735" (44.12 mm)	72 x 7	Kiwi			1628-50D*
2156 MCM	1.762" (44.75 mm)	84 x 19	Bluebird			1628-50D*
2312 MCM	1.802" (45.77 mm)	76 x 19	Thrasher			1628-50E*
2515 MCM	1.88" (47.75 mm)	76 x 19	Jorea			1628-50F*

<sup>\*</sup>Special order only. Please allow 30 days for delivery. These are not returnable.

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

#### Chicago® Grip - 1628 Series

 Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation.

#### C 20,000 lbs. (9,072 kg) Maximum Safe Load

Cat. No.	Min. to Max.	Min. to Max.	Jaw	Approx.
	Cable MCM	Cable Dia in. (mm)	Length	Wt. Each
1628-30P*	605 MCM -	.966" - 1.014"	10-3/4"	27 lbs.
	666.6 MCM	(24.54 mm - 25.76 mm)	(273 mm)	(12.27 kg)
1628-30R*	636 MCM -	1.019" - 1.063"	10-3/4"	27 lbs.
	795 MCM	(25.88 mm - 27.00 mm)	(273 mm)	(12.27 kg)
1628-30S*	715.5 MCM -	1.081" - 1.140"	10-3/4"	27 lbs.
	900 MCM	(27.46 mm - 28.96 mm)	(273 mm)	(12.27 kg)
1628-30T*	900 MCM -	1.162" - 1.196"	10-3/4"	27 lbs.
	954 MCM	(29.51 mm - 30.38 mm)	(273 mm)	(12.27 kg)
1628-30U*	1033.5 MCM -	1.212" - 1.258"	10-3/4"	27 lbs.
	1113 MCM	(30.75 mm - 31.95 mm)	(273 mm)	(12.27 kg)





#### 25,000 lbs. (11,340 kg) Maximum Safe Load

Cat. No.	Min. to Max.	Min. to Max. Cable	Jaw	Approx.
	Cable MCM	Dia. in. (mm)	Length	Wt. Each
1628-40U*	1033.5 MCM -	1.212" - 1.258"	10-3/4"	34 lbs.
	1113 MCM	(30.75 mm - 31.95 mm)	(273 mm)	(15.45 kg)
1628-40W*	1113 MCM -	1.292" - 1.317"	10-3/4"	34 lbs.
	1272 MCM	(32.82 mm - 33.45 mm)	(273 mm)	(15.45 kg)
1628-40X*	1192.5 MCM -	1.337" - 1.386"	10-3/4"	34 lbs.
	1351.5 MCM	(33.96 mm - 35.20 mm)	(273 mm)	(15.45 kg)
1628-40Y*	1351.5 MCM - 1431 MCM	1.424" - 1.427" (36.17 mm - 36.25 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40Z*	1431 MCM - 1590 MCM	1.465" - 1.504" (37.21 mm - 38.20 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40A*	1590 MCM	1.544" (39.22 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)



\*These grips are special order only. Please allow 30 days for delivery. These are not returnable.

#### Chicago® Grip — Dual Conductor

- Designed specifically for VR2<sup>®</sup> (vibration-resistant) and TransPowr<sup>®</sup> T-2<sup>®</sup> dual conductor twisted pair cables.
- Machined upper and lower jaws eliminate scoring or damage to second conductor.
- Round jaws shaped to provide maximum contact with circumference of cable and prevent cable deformation.
- Supplied with spring and locking loop handles, allows jaws to be held in open position for easier placement on cable.

#### D 25,000 lbs. (11,340 kg) Maximum Safe Load

Cat. No.	Min. to Max.	Min. to Max. Cable	Jaw	Approx.
	Cable MCM	Dia. in. (mm)	Length	Wt. Each
1628-40VRU	1113 MCM – 1192.5 MCM	1.212" - 1.258" (30.75 mm – 31.95 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)

Currently available in U size. Made to order sizes also available. Please call Klein Tools for expected delivery dates.



\*These grips are special order only. Please allow 30 days for delivery. These are not returnable.

VR2 is a registered trademark of Southwire Company. TransPowr and T-2 are registered trademarks of General Cable Technologies Corporation.





#### Chicago® Grip - 1628-50 Series

- · Round jaws shaped to provide maximum contact with circumference of cable, less likely to cause cable deformation.
- Supplied with spring and locking loop handles, allowing jaws to be held in open position for easier placement on cable.
- Removable bolt on floating jaw, secured by a slotted nut and cotter pin. Jaw provides increased cable coverage.



E

25,000 lbs. (11,340 kg) **Maximum Safe Load with bolt on jaw** 

605 - 2	le Diameter 2515 MCN 1.88" (24.5		75 mm)	<b>E</b> 25,000 lbs. (11,340 kg) with bolt on jaw					<b>E</b> 25,000 lbs. (11,340 kg) with bolt on jaw
MCM Cable Size	Diameter inches (mm)	No. of Alum. & Steel Strands	Code Word	Cat. No.	MCM Cable Size	Diameter inches (mm)	No. of Alum. & Steel Strands	Code Word	Cat. No.
605 MCM	.966" (24.54 mm)	26 x 7	Squab/ACSS	1628-50P*	1033.5 MCM	1.212" (30.81 mm)	45 x 7	Ortolan/ACSS	1628-50U*
636 MCM	.977" (24.82 mm)	24 x 7	Rook/ACSS	1628-50P*	1033.5 MCM	1.245" (31.65 mm)	54 x 7	Curlew/ACSS	1628-50U*
636 MCM	.991" (25.15 mm)	26 x 7	Grosbeak/ACSS	1628-50P*	1113 MCM	1.258" (31.95 mm)	45 x 7	Bluejay/ACSS	1628-50U*
605 MCM	.994" (25.25 mm)	30 x 7	Wood Duck/ACSS	1628-50P*	1113 MCM	1.292" (32.84 mm)	54 x 19	Finch/ACSS	1628-50W*
605 MCM	.994" (25.25 mm)	30 x 19	Teal/ACSS	1628-50P*	1192.5 MCM	1.302" (33.07 mm)	45 x 7	Bunting/ACSS	1628-50W*
666.6 MCM	1.00" (25.40 mm)	24 x 7	Flamingo/ACSS	1628-50P*	1192.5 MCM	1.337" (33.99 mm)	54 x 19	Grackle/ACSS	1628-50X*
666.6 MCM	1.014" (25.76 mm)	26 x 7	Gannet/ACSS	1628-50P*	1272 MCM	1.345" (34.16 mm)	45 x 7	Bittern/ACSS	1628-50X*
636 MCM	1.019" (25.88 mm)	30 x 19	Egret/ACSS	1628-50R*	1272 MCM	1.381" (35.10 mm)	54 x 19	Pheasant/ACSS	1628-50X*
636 MCM	1.019" (25.88 mm)	30 x 7	Scoter/ACSS	1628-50R*	1351.5 MCM	1.386" (35.20 mm)	45 x 7	Dipper/ACSS	1628-50X*
715.5 MCM	1.051" (26.70 mm)	26 x 7	Starling/ACSS	1628-50R*	1351.5 MCM	1.424" (36.17 mm)	54 x 19	Martin/ACSS	1628-50Y*
795 MCM	1.063" (27.00 mm)	45 x 7	Tern/ACSS	1628-50R*	1431 MCM	1.427" (36.25 mm)	45 x 7	Bobolink/ACSS	1628-50Y*
715.5 MCM	1.081" (27.46 mm)	30 x 19	Redwing/ACSS	1628-50S*	1431 MCM	1.465" (37.21 mm)	54 x 19	Plover/ACSS	1628-50Z*
795 MCM	1.092" (27.74 mm)	24 x 7	Cuckoo/ACSS	1628-50S*	1590 MCM	1.504" (38.15 mm)	45 x 7	Lapwing/ACSS	1628-50Z*
795 MCM	1.092" (27.76 mm)	54 x 7	Condor/ACSS	1628-50S*	1590 MCM	1.544" (39.24 mm)	54 x 19	Falcon/ACSS	1628-50A*
795 MCM	1.107" (28.14 mm)	26 x 7	Drake/ACSS	1628-50S*	1780 MCM	1.602" (40.69 mm)	84 x 19	Chukar/ACSS	1628-50B*
900 MCM	1.131" (28.73 mm)	45 x 7	Ruddy/ACSS	1628-50S*	2034.5 MCM	1.681" (42.70 mm)	72 x 7	Mockingbird/ACSS	1628-50C*
795 MCM	1.140" (28.96 mm)	30 x 19	Mallard/ACSS	1628-50S*	2167 MCM	1.735" (44.12 mm)	72 x 7	Kiwi/ACSS	1628-50D*
900 MCM	1.162" (29.51 mm)	54 x 7	Canary/ACSS	1628-50T*	2156 MCM	1.762" (44.75 mm)	84 x 19	Bluebird/ACSS	1628-50D*
954 MCM	1.165" (29.59 mm)	20 x 7	Corncrake/ACSS	1628-50T*	2312 MCM	1.802" (45.77 mm)	76 x 19	Thrasher/ACSS	1628-50E*
954 MCM	1.165" (29.59 mm)	45 x 7	Rail/ACSS	1628-50T*	2515 MCM	1.88" (47.75 mm)	76 x 19	Jorea/ACSS	1628-50F*

\*Klein Tools recommends using the 1628-50 series grips for ACSS cable. Special order only. **Application must be confirmed prior to ordering.** Please allow 30 days for delivery. Jaw must be removed to insert cable.





954 MCM

954 MCM

954 MCM

E

1.175" (29.85 mm)

1.196" (30.38 mm)

1.196" (30.38 mm)

48 x 7

54 x 7

24 x 7

#### 25,000 lbs. (11,340 kg) Maximum Safe Load with bolt on jaw

Towhee/ACSS

Cardinal/ACSS

Redbird/ACSS

1628-50T\*

1628-50T3

1628-50T<sup>3</sup>

Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Dia. in. (mm)	Jaw Length	Approx. Wt. Each
1628-50P*	605 MCM - 666.6 MCM	.966" - 1.014" (24.54 mm - 25.76 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50R*	636 MCM - 795 MCM	1.019" - 1.063" (25.88 mm - 27.00 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50S*	715.5 MCM - 900 MCM	1.081" - 1.140" (27.46 mm - 28.96 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50T*	900 MCM - 954 MCM	1.162" - 1.196" (29.51 mm - 30.38 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50U*	1033.5 MCM - 1113 MCM	1.212" - 1.258" (30.75 mm - 31.95 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50W*	1113 MCM - 1272 MCM	1.292" - 1.317" (32.82 mm - 33.45 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50X*	1192.5 MCM - 1351.5 MCM	1.337" - 1.386" (33.96 mm - 35.20 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50Y*	1351.5 MCM - 1431 MCM	1.424" - 1.427" (36.17 mm - 36.25 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50Z*	1431 MCM - 1590 MCM	1.465" - 1.504" (37.21 mm - 38.20 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50A*	1590 MCM	1.544" (39.22 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50B*	1780 MCM	1.602" (40.69 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50C*	2034.5 MCM	1.681" (42.70 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50D*	2156 MCM - 2167 MCM	1.735" - 1.762" (44.12 mm - 44.75 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50E*	2312 MCM	1.802" (45.77 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50F*	2515 MCM	1.88" (47.75 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)



Removable bolt on floating jaw, secured by a slotted nut and cotter pin. Jaw provides increased cable coverage.


**Note:** Jaw must be removed to insert cable.

VR2 is a registered trademark of Southwire Company. TransPowr and T-2 are registered trademarks of General Cable Technologies Corporation.

# ACSS/TW (Aluminum Conductor Steel Supported/Trapezoidal Wire)

For Cable Diamet <b>795 - 2627.</b>				<b>D</b> 25,000 lbs.	<b>E</b> 25,000 lbs.
	24.38 mm - 44.75 mm)			(11,340 kg)	(11,340 kg) with bolt on jaw
MCM Cable Size	Diameter inches (mm)	No. of Alum. & Steel Strands	Code Word		Cat. No
397.5 MCM	.766"828" (19.46 mm - 21.03 mm)	18 x 7	Brant/lis/Lark	1628-400*	1628-500*
556.5 MCM - 600 MCM	.891"953" (22.63 mm - 24.20 mm)	18 x 7	Maumee/ACSS/TW	1628-40M*	1628-50M*
795 MCM	.960" (24.38 mm)	17 x 7	Tern/ACSS/TW	1020 10	1628-50P*
768.2 MCM	.977" (24.82 mm)	20 x 7	Maumee/ACSS/TW		1628-50P*
795 MCM	.980" (24.89 mm)	18 x 7	Puffin/ACSS/TW		1628-50P*
795 MCM	.993" (25.22 mm)	20 x 7	Condor/ACSS/TW		1628-50P*
762.8 MCM	.990" (25.15 mm)	20 x 7	Wabash/ACSS/TW		1628-50P*
795 MCM	1.010" (25.65 mm)	20 x 7	Drake/ACSS/TW		1628-50P*
954 MCM	1.049" (26.64 mm)	30 x 7	Phoenix/ACSS/TW		1628-50R*
957.2 MCM	1.060" (26.92 mm)	32 x 7	Kettle/ACSS/TW		1628-50R*
954 MCM	1.061" (26.94 mm)	32 x 7	Rail/ACSS/TW		1628-50R*
946.7 MCM	1.077" (27.36 mm)	35 x 7	Fraser/ACSS/TW		1628-50R*
954 MCM	1.084" (27.53 mm)	20 x 7	Cardinal/ACSS/TW Snowbird/ACSS/TW		1628-50S*
1033.5 MCM 966.2 MCM	1.089" (27.66 mm) 1.092" (27.73 mm)	30 x 7	Columbia/ACSS/TW		1628-50S*
959.6 MCM	1.108" (28.14 mm)	21 x 7 22 x 7	Suwannee/ACSS/TW		1628-50S* 1628-50S*
1033.5 MCM	1.102" (27.99 mm)	32 x 7	Ortolan/ACSS/TW		1628-50S*
1033.5 MCM	1.129" (28.68 mm)	21 x 7	Curlew/ACSS/TW		1628-50S*
1113 MCM	1.129" (28.68 mm)	30 x 7	Avocet/ACSS/TW		1628-50S*
1113 MCM	1.143" (29.03 mm)	33 x 7	Bluejay/ACSS/TW		1628-50T*
1168.1 MCM	1.155" (29.34 mm)	30 x 7	Chevenne/ACSS/TW		1628-50T*
1158 MCM	1.165" (29.59 mm)	33 x 7	Genessee/ACSS/TW		1628-50T*
1192.5 MCM	1.167" (29.64 mm)	30 x 7	Oxbird/ACSS/TW		1628-50T*
1192.5 MCM	1.181" (29.99 mm)	33 x 7	Bunting/ACSS/TW		1628-50T*
1113 MCM	1.185" (30.10 mm)	38 x 19	Finch/ACSS/TW		1628-50T*
1158.4 MCM	1.196" (30.38 mm)	25 x 7	Hudson/ACSS/TW		1628-50T*
1272 MCM	1.203" (30.56 mm)	30 x 7	Scissortail/ACSS/TW		1628-50T*
1272 MCM	1.203" (30.56 mm)	30 x 7	Catawba/ACSS/TW		1628-50T*
1257.1 MCM	1.213" (30.81 mm)	35 x 7	Nelson/ACSS/TW		1628-50U*
1272 MCM	1.220" (30.99 mm)	35 x 7	Bittern/ACSS/TW		1628-50U*
1192.5 MCM 1233.6 MCM	1.225" (31.12 mm) 1.245" (31.62 mm)	38 x 19 38 x 19	Grackle/ACSS/TW Yukon/ASCSS/TW		1628-50U* 1628-50U*
1371.5 MCM	1.245 (31.70 mm)	30 x 7	Truckee/ACSS/TW		1628-50U*
1351.5 MCM	1.256" (31.90 mm)	35 x 7	Dipper/ACSS/TW		1628-50U*
1272 MCM	1.264" (32.11 mm)	39 x 19	Pheasant/ACSS/TW		1628-50U*
1359.7 MCM	1.269" (32.23 mm)	36 x 7	Mackenzie/ACSS/TW		1628-50W*
1431 MCM	1.291" (32.79 mm)	36 x 7	Bobolink/ACSS/TW		1628-50W*
1467.8 MCM	1.292" (32.82 mm)	33 x 7	St. Croix/ACSS/TW		1628-50W*
1334.6 MCM	1.293" (32.84 mm)	39 x 19	Thames/ACSS/TW		1628-50W*
1351.5 MCM	1.300" (33.02 mm)	39 x 19	Martin/ACSS/TW		1628-50W*
1455.3 MCM	1.302" (33.07 mm)	36 x 7	Miramichi/ACSS/TW		1628-50W*
1569 MCM	1.334" (33.88 mm)	33 x 7	Platte/ACSS/TW		1628-50X*
1431 MCM	1.337" (33.96 mm)	39 x 19	Plover/ACSS/TW		1628-50X*
1433.6 MCM	1.338" (33.99 mm)	39 x 19	Merrimack/ACSS/TW		1628-50X*
1557.4 MCM	1.345" (34.16 mm)	36 x 7	Potomac/ACSS/TW		1628-50X*
1590 MCM	1.358" (34.49 mm)	36 x 7	Lapwing/ACSS/TW		1628-50X*
1533.3 MCM	1.382" (35.10 mm)	39 x 19	Rio Grande/ACSS/TW		1628-50X*
1657.4 MCM 1590 MCM	1.386" (35.20 mm)	36 x 7 42 x 19	Schuylkill/ACSS/TW Falcon/ACSS/TW		1628-50X* 1628-50Y*
1622 MCM	1.408" (35.76 mm) 1.424" (36.17 mm)	39 x 19	Pecos/ACSS/TW		1628-50Y*
1758.6 MCM	1.427" (36.25 mm)	37 x 7	Pee Dee/ACSS/TW		1628-50Y*
1780 MCM	1.445" (36.70 mm)	37 x 19	Chukar/ACSS/TW		1628-50Y*
1730.6 MCM	1.445" (37.21 mm)	39 x 19	James/ACSS/TW		1628-50Z*
1949.6 MCM	1.504" (38.20 mm)	42 x 7	Athabaska/ASCC/TW		1628-50Z*
1926.9 MCM	1.545" (39.24 mm)	42 x 19	Cumberland/ACSS/TW		1628-50A*
2153.8 MCM	1.602" (40.69 mm)	64 x 19	Powder/ACSS/TW		1628-50B*
2156 MCM	1.608" (40.84 mm)	64 x 19	Bluebird/ACSS/TW		1628-50B*
2627.3 MCM	1.762" (44.75 mm)	64 x 19	Santee/ACSS/TW		1628-50D*





For Cable	Diameter				SAFE LOAD	for grip detail	
	650 MCM 28" (5.87 mn	1 - 23.57 ı	nm)	<b>A</b> 4,500 lbs (2041 kg)	8,000 lbs (3629 kg)	<b>C</b> 15,000 lbs (6803 kg)	20,000 lbs (9072 kg)
AWG or MCM Cable Size	Diameter inches (mm)	No. of Alum. Strands	Code Word	Cat. No.	Cat. No.	Cat. No.	Cat. No.
4	.231" (5.87 mm)	7	Rose	1656-20, 1656-20H and S1656-20H			
2	.292" (7.42 mm)	7	Iris	1656-20, 1656-20H and S1656-20H			
1	.328" (8.33 mm)	7	Pansy	1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H and S1656-30H		1628-16PE*	
1/0	.369" (9.36 mm)	7	Рорру	1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H and S1656-30H		1628-16PF*	
2/0	.414" (10.51 mm)	7	Aster	1656-30, 1656-30H and S1656-30H		1628-16PG*	
3/0	.465" (11.81 mm)	7	Phlox	1656-30, 1656-30H and S1656-30H		1628-16PH*	
4/0	.522" (13.25 mm)	7	Oxlip	1656-30, 1656-30H and S1656-30H		1628-16PI*	
250 MCM	.567" (14.40 mm)	7	Sneezewort		1656-40, 1656-40H and S1656-40H	1628-16PI*	
250 MCM	.574" (14.58 mm)	19	Valerian		1656-40, 1656-40H and S1656-40H	1628-16PI*	
266.8 MCM	.586" (14.88 mm)	7	Daisy		1656-40, 1656-40H and S1656-40H	1628-16PJ*	
266.8 MCM	.593" (15.05 mm)	19	Laurel		1656-40, 1656-40H and S1656-40H	1628-16PJ*	
300 MCM	.628" (15.95 mm)	19	Peony		1656-40, 1656-40H and S1656-40H	1628-16PJ*	
336.4 MCM	.665" (16.90 mm)	19	Tulip		1656-40, 1656-40H and S1656-40H	1628-16PK*	
350 MCM	.678" (17.22 mm)	19	Daffodil		1656-40, 1656-40H and S1656-40H	1628-16PK*	
397.5 MCM	.724" (18.38 mm)	19	Canna		1656-40, 1656-40H and S1656-40H	1628-16PL*	
450 MCM	.769" (19.53 mm)	19	Goldentuft		1656-50, 1656-50H and S1656-50H	1628-16PM*	
477 MCM	.792" (20.12 mm)	19	Cosmos		1656-50, 1656-50H and S1656-50H	1628-16PM*	
477 MCM	.794" (20.18 mm)	37	Syringa		1656-50, 1656-50H and S1656-50H	1628-16PM*	
500 MCM	.811" (20.60 mm)	19	Zinnia		1656-50, 1656-50H and S1656-50H	1628-16PM*	
500 MCM	.813" (20.65 mm)	37	Hyacinth		1656-50, 1656-50H and S1656-50H	1628-16PM*	
556.5 MCM	.856" (21.73 mm)	19	Dahlia		1656-50, 1656-50H and S1656-50H	1628-16PN*	1628-30N*
556.5 MCM	.858" (21.80 mm)	37	Mistletoe		1656-50, 1656-50H and S1656-50H	1628-16PN*	1628-30N*
600 MCM	.891" (22.63 mm)	37	Meadowsweet		1656-60, 1656-60H and S1656-60H		1628-300*
636 MCM	.918" (23.31 mm)	37	Orchid		1656-60, 1656-60H and S1656-60H		1628-300*
650 MCM	.928" (23.57 mm)	37	Heuchera		1656-60, 1656-60H and S1656-60H		1628-300*

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

AWARNING: When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

See facing page

BAAVIBAUBA OAFE LOAD

AWARNING: Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

<sup>&</sup>quot;S" is for spring. "H" is for hot latch.
\*Special order only. Please allow 30 days for delivery. These are not returnable.

#### Chicago® Grip - 1656 Series

- Round, smooth inside jaw contour on this series of grips is recommended for bare AAC.
- Smooth jawed grips with maximum contact are less likely to cause cable deformation.



### A

#### 4,500 lbs. (2,041 kg) Maximum Safe Load

Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable AWG	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1656-20	1656-20H	S1656-20H	4 - 1/0	.231"369" (5.87 mm - 9.37 mm)	4" (102 mm)	3 lbs. (1.36 kg)
1656-30	1656-30H	S1656-30H	1- 4/0	.328"522" (8.33 mm - 13.26 mm)	4-3/4" (121 mm)	3.75 lbs. (1.70 kg)

#### В

#### 8,000 lbs. (3,629 kg) Maximum Safe Load

Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1656-40	1656-40H	S1656-40H	250 MCM - 397.5 MCM	.567"724" (14.40 mm - 18.39 mm)	5-1/2" (140 mm)	8.30 lbs. (3.76 kg)
1656-50	1656-50H	S1656-50H	450 MCM - 556.5 MCM	.769"858" (19.53 mm - 21.79 mm)	5-1/2" (140 mm)	8.30 lbs. (3.76 kg)
1656-60	1656-60H	S1656-60H	600 MCM - 650 MCM	.891"928" (22.63 mm - 23.57 mm)	5-1/2" (140 mm)	8.20 lbs (3.71 kg)

#### Chicago® Grip - 1628-16P and 1628-30 Series

- Designed for large-diameter AAC cables.
- Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation.

#### C

#### 15,000 lbs. (6,803 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable AWG or MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-16PE*	1	.328" (8.33 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PF*	1/0	.369" (9.37 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PG*	2/0	.414" (10.52 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PH*‡	3/0	.465" (11.81 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PI*	250 MCM	.567"574" (14.40 mm - 14.58 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PJ*	266.8 MCM - 300 MCM	.586"628" (14.88 mm - 15.95 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PK*	336.4 MCM - 350 MCM	.665"678" (16.89 mm - 17.22 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PL*	397.5 MCM	.724" (18.39 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PM*	450 MCM - 500 MCM	.769"813" (19.53 mm - 20.65 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)
1628-16PN*	556.5 MCM	.856"858" (21.74 mm - 21.79 mm)	7-1/4" (184 mm)	17 lbs. (7.73 kg)




#### 20,000 lbs. (9,072 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-30N**	556.5 MCM	.856"858" (21.74 mm - 21.79 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-300**	600 MCM - 650 MCM	.891"928" (22.63 mm - 23.57 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)

<sup>\*\*</sup> Maximum safe stringing tension 12,500 lbs to minimize cable deformation.







<sup>\*</sup>These grips are special order only. Please allow 30 days for delivery. These are not returnable.



See facing page for grip details. **For Cable Diameter** 

700 - 2500 MCM .963" - 1.823" (24.46 mm - 46.30 mm)			<b>C</b> 20,000 lbs (9,072 kg)	<b>D</b> 25,000 lbs (11,340 kg)	<b>E</b> 25,000 lbs. (11,340 kg)	
MCM Cable Size	Diameter inches (mm)	No. of Alum. & Steel Strands	Code Word	Cat. No.	Cat. No.	with bolt on jaw  Cat. No.
700 MCM	.963" (24.46 mm)	37	Verbena	1628-30P*		1628-50P*
700 MCM	.964" (24.49 mm)	61	Flag	1628-30P*		1628-50P*
715.5 MCM	.974" (24.73 mm)	37	Violet	1628-30P*		1628-50P*
715.5 MCM	.975" (24.76 mm)	61	Nasturtium	1628-30P*		1628-50P*
750 MCM	.997" (25.32 mm)	37	Petunia	1628-30P*		1628-50P*
750 MCM	.998" (25.35 mm)	61	Cattail	1628-30P*		1628-50P*
795 MCM	1.026" (26.07 mm)	37	Arbutus	1628-30R*		1628-50R*
795 MCM	1.028" (26.11 mm)	61	Lilac	1628-30R*		1628-50R*
800 MCM	1.029" (26.14 mm)	37	Fuchsia	1628-30R*		1628-50R*
800 MCM	1.031" (26.19 mm)	61	Heliotrope	1628-30R*		1628-50R*
874.5 MCM	1.076" (27.37 mm)	37	Anemone	1628-30R*		1628-50R*
874.5 MCM	1.077" (27.36 mm)	61	Crocus	1628-30R*		1628-50R*
900 MCM	1.092" (27.74 mm)	37	Cockscomb	1628-30S*		1628-50S*
954 MCM	1.124" (28.55 mm)	37	Magnolia	1628-30S*		1628-50S*
954 MCM	1.126" (28.60 mm)	61	Goldenrod	1628-30S*		1628-50S*
1000 MCM	1.152" (29.26 mm)	61	Camellia	1628-30T*		1628-50T
1000 MCM	1.152" (29.26 mm)	37	Hawkweed	1628-30T*		1628-50T*
1033.5 MCM	1.170" (29.71 mm)	37	Bluebell	1628-30T*		1628-50T*
1033.5 MCM	1.172" (29.76 mm)	61	Larkspur	1628-30T*		1628-50T*
1113 MCM	1.216" (30.88 mm)	61	Marigold	1628-30U*	1628-40U*	1628-50U*
1192.5 MCM	1.258" (31.96 mm)	61	Hawthorn	1628-30U*	1628-40U*	1628-50U*
1272 MCM	1.297" (32.94 mm)	61	Narcissus		1628-40W*	1628-50W*
1351.5 MCM	1.339" (34.02 mm)	61	Columbine		1628-40X*	1628-50X*
1431 MCM	1.379" (35.02 mm)	61	Carnation		1628-40X*	1628-50X*
1510.5 MCM	1.417" (35.98 mm)	61	Gladiolus		1628-40Y*	1628-50Y*
1590 MCM	1.454" (36.93 mm)	61	Coreopsis		1628-40Z*	1628-50Z*
1750 MCM	1.524" (38.72 mm)	61	Jessamine		1628-40A*	1628-50A*
2000 MCM	1.630" (41.41 mm)	91	Cowslip			1628-50B*
2250 MCM	1.729" (43.92 mm)	91	Sagebrush			1628-50D*
2500 MCM	1.823" (46.30 mm)	91	Lupine			1628-50E*

<sup>\*\*</sup> Maximum safe stringing tension 12,500 lbs to minimize cable deformation.
\* Special order. Please allow 30 days for delivery. These are not returnable.

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

AWARNING: When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

AWARNING: Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

#### Chicago® Grip - 1628 Series

 Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation.

#### C 20,000 lbs. (9,072 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-30P*	700 MCM - 750 MCM	.963"998" (24.46 mm - 25.35 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-30R*	795 MCM - 874.5 MCM	1.026" - 1.077" (26.06 mm - 27.36 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-30S*	900 MCM - 954 MCM	1.092" - 1.126" (27.74 mm - 28.60 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-30T*	1000 MCM - 1033.5 MCM	1.152" - 1.172" (29.26 mm - 29.77 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)
1628-30U*	1113 MCM - 1192.5 MCM	1.216" - 1.258" (30.89 mm - 31.95 mm)	10-3/4" (273 mm)	27 lbs. (12.27 kg)



#### **D** 25,000 lbs. (11,340 kg) Maximum Safe Load

Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-40U*	1113 MCM - 1192.5 MCM	1.216" - 1.258" (30.89 mm - 31.95 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40W*	1272 MCM	1.297" (32.94 mm )	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40X*	1351.5 MCM - 1431 MCM	1.339" - 1.379" (34.01 mm - 35.03 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40Y*	1510.5 MCM	1.417" (35.99 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40Z*	1590 MCM	1.454" (36.93 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-40A*	1750 MCM	1.524" (38.71 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)



# 25,000 lbs. (11,340 kg) Maximum Safe Load with bolt on jaw

	•			
Cat. No.	Min. to Max. Cable MCM	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
1628-50P*	700 MCM - 750 MCM	.963"998" (24.46 mm - 25.35 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50R*	795 MCM - 874.5 MCM	1.026" - 1.077" (26.06 mm - 27.36 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50S*	900 MCM - 954 MCM	1.092" - 1.126" (27.74 mm - 28.60 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50T*	1000 MCM - 1033.5 MCM	1.152" - 1.172" (29.26 mm - 29.77 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50U*	1113 MCM - 1192.5 MCM	1.216" - 1.258" (30.89 mm - 31.95 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50W*	1272 MCM	1.297" (32.94 mm )	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50X*	1351.5 MCM - 1431 MCM	1.339" - 1.379" (34.01 mm - 35.03 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50Y*	1510.5 MCM	1.417" (35.99 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50Z*	1590 MCM	1.454" (36.93 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50A*	1750 MCM	1.524" (38.71 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50B*	2000 MCM	1.630" (41.40 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50D*	2250 MCM	1.729" (43.92 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)
1628-50E*	2500 MCM	1.823" (46.30 mm)	10-3/4" (273 mm)	34 lbs. (15.45 kg)

\*These grips are special order only. Please allow 30 days for delivery. These are not returnable.



 Removable bolt on floating jaw, secured by a slotted nut and cotter pin. Jaw provides increased cable coverage.

**Note:** Jaw must be removed to insert cable.





## Copper - Chicago® Grips

#### Bare Stranded Chicago® Grips – 1656 Series

- Round, smooth inside jaw contour on this series of grips is ideal for stranded-copper cables.
- Smooth jaws grip with maximum contact are less likely to cause cable deformation.





Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
4,500 lbs. (2	2,041 kg) Maxii	num Safe Load			
1656-20	1656-20H	S1656-20H	.20"40" (5.08 mm - 10.16 mm)	4" (102 mm)	3 lbs. (1.36 kg)
1656-30	1656-30H	S1656-30H	.31"53" (7.87 mm - 13.46 mm)	4 3/4" (121 mm)	3.75 lbs (1.70 kg)
8,000 lbs. (3	3,629 kg) Maxii	num Safe Load			
1656-40	1656-40H	S1656-40H	.53"74" (13.46 mm - 18.80 mm)	5 1/2" (140 mm)	8.30 lbs (3.76 kg)
1656-50	1656-50H	S1656-50H	.74"86" (18.80 mm - 21.84 mm)	5 1/2" (140 mm)	8.30 lbs (3.76 kg)
1656-60	1656-60H	S1656-60H	.86"96" (21.84 mm - 24.38 mm)	5 1/2" (140 mm)	8.20 lbs (3.71 kg)



# Weatherproof Stranded and Solid Chicago® Grips — 1611 Series

- Round inside jaw contour for weatherproof coated wire.
- Notches in jaw provide firm grip on insulation.



Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each			
4,500 lbs. (2,041 kg) Maximum Safe Load						
1611-20	.20"40" (5.08 mm - 10.16 mm)	4-3/16" (106 mm)	3 lbs. (1.36 kg)			
1611-30	.31"53" (7.87 mm - 13.46 mm)	4-3/4" (121mm)	3.75 lbs (1.70 kg)			
8,000 lbs. (3,629 kg) Maxim	um Safe Load					
1611-40	.53"74" (13.46 mm - 18.80 mm)	5-11/16" (144 mm)	7.75 lbs (3.52 kg)			
1611-50	.74"86" (18.80 mm - 21.84 mm)	5-11/16" (144 mm)	7.75 lbs (3.52 kg)			
Note: Due to various types of we	Note: Due to various types of weatherproof coatings available, selection of proper grips is determined by outside diameter of cable.					

#### PVC-Covered Chicago® Grips - 1659 Series

- Specially machined serpentine jaws allow insulated conductor to be inserted through jaws.
- Eliminates necessity of stripping insulation from conductor.
- Round inside-jaw contour.



Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each		
4,500 lbs. (2,041 kg) Maximum Safe Load					
1659-20	.20"42" (5.08 mm - 10.67 mm)	4-3/16" (106 mm)	3 lbs. (1.36 kg)		
1659-30	.31"50" (7.87 mm - 12.70 mm)	4-3/4" (121 mm)	3.75 lbs (1.70 kg)		
8,000 lbs.	8,000 lbs. (3,629 kg) Maximum Safe Load				
1659-40	.49"79" (12.45 mm - 20.07 mm)	5-11/16" (144 mm)	7.75 lbs (3.52 kg)		
1659-50	.79" - 1.01" (20.07 mm - 25.56 mm)	5-11/16" (144 mm)	7.75 lbs (3.52 kg)		



All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.





242

## Steel Strand - Chicago® Grips

# Bell System B, L, and H Chicago $^{\odot}$ Grips - 1628, 1659, 1684 & 1692 Series

- All are equipped with chain, toggle and shackle keeps the grip from falling off of cable.
- 1659 5AT is similar to Bell-System type "B" Strand Puller. Designed to pull 1/4" (6.35 mm) figure-8 telephone cable. Also has serpentine jaw.
- 1684 5AT is identical to Bell-System type "L" Strand Puller.
- 1628 16AT is identical to Bell-System type "H" Strand Puller.

Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each			
5,000 lbs. (2,268 kg) Maximum Safe Load						
1659-5AT ("B" Strand Puller)	.20"37" (5.08 mm - 9.40 mm)	5" (127mm)	6.70 lbs. (3.03 kg)			
8,000 lbs. (3,629 kg) Ma	8,000 lbs. (3,629 kg) Maximum Safe Load					
1684-5AT ("L" Strand Puller)	.218"550" (5.54 mm - 13.97 mm)	5" (127mm)	6.9 lbs (3.13 kg)			
1692-5AT ("L" Strand Puller)	.218"550" (5.54 mm - 13.97 mm)	5" (127mm)	6.6 lbs (3.00 kg)			
15,000 lbs. (6,803 kg) Maximum Safe Load						
1628-16AT ("H" Strand Puller)	.31"62" (7.87 mm - 15.75 mm)	7 1/4" (184 mm)	15.80 lbs (7.16 kg)			
*1602 EAT (larger elemning	a force than 1604 EAT)					

<sup>\*1692-5</sup>AT (larger clamping force than 1684-5AT)





Cat. No.	Hot Latch Model No.	Hot Latch/Spring Model No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
4,500 lbs. (2,041 kg) Maximum Safe	Load				
1613-40	1613-40H	S1613-40H	.12"37" (3.05 mm - 9.40 mm)	4-3/16" (106 mm)	3 lbs. (1.36 kg)
8,000 lbs. (3,629 kg) Maximum Safe	Load				
1684-5F	NA	NA	.16"550" (4.06 mm - 13.97 mm)	5" (127 mm)	6.25 lbs. (2.84 kg)
1684-5	1684-5H	S1684-5H	.218"550" (5.54 mm - 13.97 mm)	5" (127 mm)	6.25 lbs. (2.84 kg)
1692-5 (larger clamping force than 1684-5)	NA	NA	.218"550" (5.54 mm - 13.97 mm)	5" (127 mm)	6.40 lbs. (2.89 kg)
8,000 lbs. (3,629 kg) Maximum Safe	Load – EHS Specific	+			
1684-74 (Includes curved jaw)	NA	S1684-74H	.218"550" (5.54 mm - 13.97 mm)	5" (127 mm)	6.30 lbs. (2.85 kg)
15,000 lbs. (6,803 kg) Maximum Safe	e Load				
1628-16	NA	NA	.31"62" (7.87 mm - 15.75 mm)	7-1/4" (184 mm)	15.30 lbs. (7.00 kg)
1628-17	NA	NA	.50"75" (12.70 mm - 19.05 mm)	7-1/4" (184 mm)	16.30 lbs. (7.40 kg)
1628-18	NA	NA	.75" - 1.00" (19.05 mm - 25.40 mm)	7-1/4" (184 mm)	15.70 lbs. (7.10 kg)



## Copper/Steel Strand — Chicago® Grips

#### **Bare Wire** Chicago® Grips - 1613 Series

- Designed for working with solid and stranded bare wire from .08" (2 mm) to .20" (5.1 mm).
- Lightweight, cost-effective grip.
- Single "V" groove jaw.





Cat. No.	Minimum	Maximum	Maximum	Jaw	Approx.
	Cable	Cable	Safe Load	Length	Weight Each
1613-30	12 B&S solid .08" (2.03 mm)	4 B&S solid .20" (5.08 mm)	1500 lbs. (680 kg)	3" (76 mm)	1.50 lbs. (.68 kg)

## Steel Strand — Haven's® Grips

#### **Messenger and Guy Strand** Haven's® Grips - 1604 Series

- Designed for use when light, compact grip is desired and where cable deformation is not a factor.
- Gripping pressure of the knurled law is applied to 1/4" (6.35 mm) cable area.





1604-20

1625-20

Cat. No.	Latch Model	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each		
2,500 lbs.	2,500 lbs. (1,134 kg) Maximum Safe Load					
1604-10	NA	.06"25" (1.52 mm - 6.35 mm)	N/A	1 lb. (.45 kg)		
5,000 lbs.	5,000 lbs. (2,268 kg) Maximum Safe Load					
1604-20	1604-20L	.125"50" (3.18 mm - 12.70 mm)	N/A	2.08 lbs. (1.14 kg)		





- Designed for use when light, compact grip is desired and where cable deformation is not a factor.
- Gripping pressure of the knurled jaw is applied to 1/4" (6.35 mm) cable area.
- All 1625 series have a swing latch to help hold cable in the jaw.





Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
8,000 lbs. (3	3,629 kg) Maximum Safe Load		
1625-20	.28"75" (7.11 mm - 19.05 mm)	N/A	4 lbs. (1.81 kg)
1625-20 7/8	.38"88" (9.65 mm - 22.35 mm)	N/A	4 lbs. (1.81 kg)
1625-20 1	.50" - 1.00" (12.70 mm - 25.40 mm)	N/A	4 lbs. (1.81 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

AWARNING: When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.



## **Wide Range of Cables**

## Parallel Jaw Grips - KT4500, KT4600 and KT4800 Series



- The KT4500, KT4600 and KT4800 Series feature a round serrated jaw.
- KT4501, KT4502, KT4601, KT4602, KT4801, KT4802 are supplied with hot latches.
- Hot latch closes automatically to guard against grip accidentally disengaging from wire.
- Large opening in the handle to accommodate a wide variety of hooks on hoists, winches and tackle blocks.

Cat. No.	Min. to Max. Cable Diameter inches (mm)	Hot Latch	Spring	Locking Handle	Jaw Length	Approx. Weight Each
5,000 lbs. (2,2	268 kg) Maximum Safe Load	·				
KT4500	.180"600" (4.57 mm - 15.2 mm)		•		4" (101.3 mm)	3.75 lbs. (1.70 kg)
KT4501	.180"600" (4.57 mm - 15.2 mm)	•	•	•	4" (101.3 mm)	3.75 lbs. (1.70 kg)
KT4502	.180"600" (4.57 mm - 15.2 mm)	•			4" (101.3 mm)	3.75 lbs. (1.70 kg)
KT4650	.160"900" (4.00 mm - 23.0 mm)		•		4-1/2" (114 mm)	4.90 lbs. (2.22 kg)
KT4652	.160"900" (4.00 mm - 23.0 mm)	•	•		4-1/2" (114 mm)	4.90 lbs. (2.22 kg)
10,000 lbs. (4	,536 kg) Maximum Safe Load					
KT4600	.300"800" (7.62 mm - 20.3 mm)		•		5" (127 mm)	7 lbs. (3.18 kg)
KT4601	.300"800" (7.62 mm - 20.3 mm)	•	•	•	5" (127 mm)	7 lbs. (3.18 kg)
KT4602	.300"800" (7.62 mm - 20.3 mm)	•			5" (127 mm)	7 lbs. (3.18 kg)
12,000 lbs. (5	,443 kg) Maximum Safe Load					<u> </u>
KT4800	.700" - 1.25" (17.8 mm - 31.8 mm)		•		5-1/8" (130 mm)	9 lbs. (4.1 kg)
KT4801	.700" - 1.25" (17.8 mm - 31.8 mm)	•	•	•	5-1/8" (130 mm)	9 lbs. (4.1 kg)
KT4802	.700" - 1.25" (17.8 mm - 31.8 mm)	•			5-1/8" (130 mm)	9 lbs. (4.1 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.





Cat. No.

1685-20

1685-31

# EST 1857

## **Wide Range of Cables**

#### Parallel Jaw Grips - 1685 Series

- Lightweight, compact grips pull an exceptionally wide range of cable types and sizes.
- Designed with a round inside-jaw contour for maximum contact to minimize cable deformation.
- Lower jaw is serrated to firmly grip insulated cables and conductors.
- Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable.
- Large-diameter eye accommodates large hooks on hoists, winches and tackle blocks.

Min. to Max. Cable


4,500 lbs. (2,041 kg) Maximum Safe Load

7,500 lbs. (3,400 kg) Maximum Safe Load

Diameter inches (mm)

.157" - .875" (4 mm - 22 mm)

.625" - 1.250" (16 mm - 32 mm)



Parallel Jaw Grips –	1686-10	1686-20	1671-10 and	1672-10

- Longer jaws achieve a firm hold, reducing possibility of slippage and deformation to cable.
- Designed with a Double V jaw contour, a latch, plus a large-diameter eye that accommodates large hooks on hoists, winches, and tackle blocks.
- When latch is closed, it helps maintain cable position in grip jaws.

Cat. No.	Min. to Max. Cable Diameter inches (mm)	Jaw Length	Approx. Weight Each
10,000 lbs	. (4,536 kg) Maximum Safe Lo	ad	
1686-10	.20"40" (5.08 mm - 10.16 mm)	4-3/8" (111 mm)	5 lbs. (2.27 kg)
1686-20 Knurled Jaw	.20"40" (5.08 mm - 10.16 mm)	4-3/8" (111 mm)	5 lbs. (2.27 kg)
1671-10	.37"75" (9.40 mm - 19.05 mm)	4-3/8" (111 mm)	5 lbs. (2.27 kg)
1672-10 Knurled Jaw	.37"75" (9.40 mm - 19.05 mm)	4-3/8" (111 mm)	5 lbs. (2.27 kg)



All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**AWARNING:** Do not exceed rated capacity.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

246

## **Interchangeable Jaw Grips & Liners**

#### **Interchangeable Jaw Grips & Liners**

- Constructed of high strength alloy steel, hot forged, heat treated, and galvanized for toughness, strength and corrosion resistance.
- Suitable for Optical Ground Wire (OPGW) conductors .236" to .906" (6 mm - 23 mm) (Cat. No. 1628-80).
- Offers a full range of interchangeable liners to be inserted between the upper and lower jaws of the grip.







Lower liner – Aluminum Upper liner – Aluminum (Cat. No. 1628-60)

Lower liner – Polyurethane (provides cushioning for the optical cable)

Üpper liner – Aluminum (Cat. No. 1628-80)

 Liners are made to order. Call customer service with details of cable diameter, cable type and working load requirements for availability and lead time.

Cat. No.	Description	Cable Diameter Range	Maximum Working Load	Recommended For:	Weight
1628-60	1628-60 grip body only	.394" to 1.614" (10 mm to 41 mm)	6,750 lbs. (3060 kg.)	conductor cable	38 lbs. (17 kg.)
1628-80	1628-80 OPGW grip body only	.236" to .906" (6 mm to 23 mm)	6,750 lbs. (3060 kg.)	OPGW	15 lbs. (7 kg.)

**AWARNING**: Grips are to be used for temporary installation, not for permanent anchorage.

**AWARNING**: When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

AWARNING: Do not exceed capacity.

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.






## Accessories

#### **Grip-Cleaning Brush Set**

- Set of four wire-bristle brushes designed for cleaning Klein wire and cable-pulling grips.
- Brushes have stiff wire bristles.
- Available in round and square shapes and two lengths for efficient cleaning of different jaw configurations.
- Semi-flexible steel shafts set into comfortable wooden handles provide the necessary reach into grip jaws.

Cat. No.	Set Contains			Weight (lbs.)
25450				1.00
	Description	Bristle Diameter and Length	Overall Length	
	round-bristle	3/8" x 3" (10 mm x 76 mm)	12" (305 mm)	
	square-bristle	3/8" x 3" (10 mm x 76 mm)	12" (305 mm)	
	round-bristle	1-9/16" x 5" (40 mm x 127 mm)	14" (356 mm)	
	square-bristle	1-9/16" x 5" (40 mm x 127 mm)	14" (356 mm)	







248


## **Introduction – Wire-Mesh Grips**

Klein mesh pulling-grips are used for pulling overhead or underground cable, for stringing service or communication lines into buildings, for pulling wire through conduit, and for general underground construction.

Klein grips may be used for pulling bare or insulated wires, and wire rope. They install quickly and easily, and are designed to pass readily through ducts, conduit, blocks, and sheaves.

Klein grips are reusable and do not damage the cable because pulling tension remains uniform along the length of the grip. The mesh will fit either a single cable, or a bundle of cables.

Klein pulling grips are woven of galvanized steel – strong and long lasting.



#### **General Application Information**

**KPJ** junior-duty series is used for small-job requirements where pulling tensions are low. Typical uses are to connect insulated building wire bundles to pulling tape, and pull through conduit.

**KPL** light duty grips are economical for applications such as industrial plant wiring and rewiring jobs, and in underground electrical construction where pulling tensions are low.

KSRK light-duty slack-pulling grips are split mesh, single-weave design with rod closure for quick installation. Application areas similar to KSSK series, except mesh lengths are shorter and are for lower pulling loads.

**KPM** medium-duty grips are flexible and easily handled, ideal for use where the exceptional strength of heavy-duty grips is not required.

**KSCK** medium-duty slack-pulling grips with closed double-weave mesh are used for final placement of underground cable where cable end is available, or for removing cable. Standard lengths are used in restricted space for short pulls. Where space is not restricted, longer lengths are used for higher pulling loads.

KSSK medium-duty slack-pulling grip applications are similar to the KSCK series except they are used where cable end is not available. Double-weave split mesh has lace closure.

**KP** heavy-duty grip series are recommended for underground installations.

**KPS** heavy-duty grip series are also recommended for underground installations. An additional feature of the KPS includes "rotating eye" to allow twists in the cable to spin out during slack periods.

#### **Prefix Letter Code**

KPJ	Pulling, Junior-Duty, Closed-Mesh,
	Single-Weave, Light Duty, Flexible Eye

**KPL** Pulling, Closed-Mesh, Single-Weave, Flexible Eye

**KSRK** Slack-Pulling, Light-Duty, Split-Mesh,

Single-Weave, Rod Closure, Offset Flexible Eve

**KPM** Pulling, Medium-Duty, Closed-Mesh, Double-Weave, Flexible Eye


**KSCK** Slack-Pulling, Meduim Duty, Closed-Mesh. Double-Weave. Offset Flexible Eve

**KSSK** Slack-Pulling, Meduim Duty, Split-Mesh, Double-Weave, Lace Closure, Offset Flexible Eve

ΚP Pulling, Heavy-Duty, Closed-Mesh.

Double-Weave, Flexible Eve

**KPS** Pulling, Heavy-Duty, with Rotating Eye, Closed-Mesh, Double-Weave




#### **Catalog Number Explanation**

KPS	_	050	_	2
Grip Type* and Mesh		Cat. No.** Size Code		Final Digit, if any, refers to mesh length range or actual dimension.

\* See Prefix Letter Code explanation.
\*\* On Junior-duty grips, initial digit "0" is omitted in Cat. No.

#### **Example:**

Cat. No. KPS-050-2 is a heavy-duty pulling grip with a rotating eye, for use with cable diameters from .50" to .61", with medium-length mesh.







## **Introduction – Wire-Mesh Grips**


#### How to select proper grip eye and mesh type

There are three basic styles of pulling grips, together with a choice of wire mesh types and lengths to meet a wide variety of pulling requirements.

#### 1. Flexible Eve: Closed Mesh

#### KPJ/KPL/KPM/KP

This pulling-grip eye allows maximum flexibility to follow the line of pull, and is used when the end of the cable is available. Mesh selection depends on the weight of the material being pulled. Closed-mesh. single weave, flexible-eye grips are offered in lengths for junior-duty and light-duty use; closed-mesh, double-weave, flexible-eye grips are offered for medium-duty and heavy-duty use.



#### 2. Rotating Eve: Closed Mesh

#### **KPS**

Recommended for heavier pulling jobs and underground wiring, this pulling grip eye is furnished on double-weave mesh grips in a wide range of lengths. The rotating eye compensates for pulling torque, relieving strain on the cable. Rotating-eye grips should not be used on rope or as a swivel.



#### 3. Offset Flexible Eve: Split and Closed Mesh

#### KSRK/KSCK/KSSK

These slack-pulling grips come in three styles:

KSRK single-weave split-mesh with rod closure (light duty, where cable end is not available),

KSCK double-weave closed-mesh (for medium duty, where the end of the cable is available),

**KSSK** double-weave split-mesh with lace closure (medium duty, where cable end is not available).



#### How grips are attached to cable

#### Closed-mesh grips

Closed-mesh grips simply slip over the cable where the cable end is accessible.

#### Split-mesh grips

Split-mesh grips are used when the end of the cable is not available. The grip is folded around the cable, and secured with a wire lace or steel rod (supplied with the grip) as follows:

#### 1. Split mesh with lace closure

Start at the lead end of the grip, threading the lace through the first two loops of the split, then pulling it through until ends are centered evenly. Cross the lace ends and thread through next two loops, and so on down the grip. Do not pull lacing too tight. Spacing of laced closure should be about the same as the mesh weave. When the end of the grip is reached, twist lacing strands tightly together; wrap ends of lace around grip, and twist again to secure. Excess may be cut off.

#### 2. Split mesh with rod closure

Split-mesh grips with rod closure can be quickly installed. Simply wrap the grip around the cable, then thread the rod through the loops, using a cork-screw motion. To remove, pull the rod out, and the grip is ready for re-use.

#### **Design Strength**

Applications and conditions of use for Klein mesh pulling grips vary so widely that it is impossible to set any meaningful standard for "breaking strength."

With wire-mesh pulling grips, the holding power achieved is directly related to the length of mesh. The longer the mesh, the firmer the grip on the cable. For smaller-diameter cable, or where the weight to be pulled is less, short mesh grips will serve the purpose.



## **Introduction – Wire-Mesh Grips**

#### How to select the proper pulling grip for your application

- Select the proper pulling-grip series (Prefix Letter Code...e.g. KPS) based on the "General Application Information" descriptions in the Wire-Mesh Grips Introduction on preceding pages.
- 2. Select grip size based on the outside diameter or circumference of the cable(s) to be pulled. Refer to reference tables (on this and following page) for convenience in determining cable diameters.
- 3. Use Pulling-Grip Selection Tables (on this and following page) to determine the "Size" portion of the Catalog Number for the cable diameter required. In the ordering tables (see following pages) this "Size" code is incorporated within the catalog number under the various grip-type classifications.

#### Table 1

#### Pulling Grip Selection Table for One or More Cables of Equal Diameter to Be Pulled in One Grip

- 1. Read across on top line for number of cables in one grip.
- 2. Read down for diameter of each cable.
- 3. Use Cat. No. size code to select catalog number of the required size grip.

#### **Example:**

3 Cables, each with diameter of 1.31" use grip with Cat. No. Size Code 250.

#### Cable Diameters in Decimal Inches

1 Cable	2 Cables	3 Cables	4 Cables	5 Cables	6 & 7 Cables	8 Cables	g Cables	Cat. No. Size Code	Grip Diam. Range
0.25-0.37	0.16-0.25	0.15-0.22	0.12-0.20	0.11-0.14	0.10-0.11	0.09-0.10	0.06-0.09	025	0.12-0.37
0.37-0.50	0.25-0.36	0.22-0.33	0.20-0.28	0.14-0.25	0.11-0.25	0.10-0.20	0.09-0.19	037	0.37-0.50
0.50-0.62	0.27-0.36	0.26-0.33	0.24-0.28	0.21-0.25	0.19-0.22	0.17-0.20	0.15-0.19	050	0.50-0.62
0.62-0.75	0.36-0.45	0.33-0.36	0.28-0.31	0.25-0.29	0.22-0.26	0.20-0.23	0.19-0.22	062	0.62-0.75
0.75-1.00	0.45-0.60	0.36-0.49	0.31-0.42	0.29-0.38	0.26-0.34	0.23-0.31	0.22-0.31	075	0.75-1.00
1.00-1.25	0.60-0.76	0.49-0.63	0.42-0.54	0.38-0.48	0.34-0.43	0.31-0.39	0.29-0.36	100	1.00-1.25
1.25-1.50	0.76-0.91	0.63-0.76	0.54-0.65	0.48-0.58	0.43-0.52	0.39-0.46	0.36-0.43	125	1.25-1.50
1.50-1.75	0.91-1.08	0.76-0.89	0.65-0.77	0.58-0.67	0.52-0.60	0.46-0.54	0.43-0.49	150	1.50-1.75
1.75–2.00	1.08-1.23	0.89-1.02	0.77-0.88	0.67-0.77	0.60-0.69	0.54-0.62	0.49-0.57	175	1.75-2.00
2.00-2.50	1.23-1.54	1.02-1.28	0.88-1.10	0.77-0.96	0.69-0.86	0.62-0.77	0.57-0.72	200	2.00-2.50
2.50-3.00	1.54-1.84	1.28-1.53	1.10-1.32	0.96-1.16	0.86-1.03	0.77-0.93	0.72-0.86	250	2.50-3.00
3.00-3.50	1.84-2.15	1.53-1.79	1.32-1.54	1.16-1.35	1.03-1.20	0.93-1.08	0.86-1.00	300	3.00-3.50
3.50-4.00	2.15-2.45	1.79-2.05	1.54-1.76	1.35-1.54	1.20-1.37	1.08-1.24	1.00-1.14	350	3.50-4.00

#### Cable Diameters in Fractional Inches

Oubic Diamic	Cable Dialifeters III Fractional Inches									
1 Cable	2 Cables	3 Cables	4 Cables	5 Cables	6 & 7 Cables	8 Cables	g Cables	Cat. No. Size Code	Grip Diam. Range	
1/4-3/8	1/64-1/4	5/32-7/32	1/8-13/64	7/64-9/64	3/32-7/64	3/32-7/64	1/16-3/32	025	1/8-3/8	
3/8-1/2	1/4-23/64	7/32–21/64	13/64-9/32	9/64-1/4	7/64–1/4	7/64-13/64	3/32-3/16	037	3/8-1/2	
5/8-3/4	23/64-29/64	21/64-23/64	9/32-5/16	1/4-19/64	7/32-17/64	13/64-15/64	3/16-7/32	050	1/2-5/8	
1/2-5/8	17/64-23/64	7/64–21/64	15/64-9/32	7/32-1/4	3/16–7/32	11/64-13/64	5/32-3/16	062	5/8-3/4	
3/4–1	29/64-39/64	23/64-31/64	5/16-27/64	19/64-3/8	17/64-11/32	15/64-5/16	7/32-5/16	075	3/4–1	
1-1-1/4	39/64-49/64	31/64–5/8	27/64-35/64	3/8-31/64	11/32–7/16	5/16-25/64	19/64-23/64	100	1-1-1/4	
1-1/4-1-1/2	49/64-29/32	5/8-49/64	35/64–21/32	31/64-37/64	7/16-33/64	25/64-15/32	23/64-7/16	125	1-1/4-1-1/2	
1-1/2-1-3/4	29/32-1-5/64	49/64-57/64	21/32-49/64	37/64-43/64	33/64-39/64	15/32-35/64	7/16-31/64	150	1-1/2-1-3/4	
1-3/4-2	1-5/64-1-15/64	57/64–1-1/64	49/64-7/8	43/64-49/64	39/64-11/16	35/64-5/8	31/64-37/64	175	1-3/4-2	
2-2-1/2	1-15/64-1-35/64	1-1/64-1-9/32	7/8-1-3/32	49/64-31/32	11/16-55/64	5/8-49/64	37/64-23/32	200	2-2-1/2	
2-1/2-3	1-35/64-1-27/32	1-9/32-1-17/32	1-3/32-1-21/64	31/32-1-5/32	55/64-1-1/32	49/64-15/16	23/32-55/64	250	2-1/2-3	
3-3-1/2	1-27/32-2-5/32	1-17/32–1-51/64	1-21/64-1-35/64	1-5/32-1-23/64	1-1/32-1-13/64	15/16–1-5/64	55/64-1	300	3-3-1/2	
3-1/2-4	2-5/32-2-29/64	1-51/64-2-3/64	1-35/64-1-49/64	1-23/64-1-35/64	1-13/64-1-3/8	1-5/64-1-15/64	1-1-9/64	350	3-1/2-4	





## **Wire-Mesh Grips**


Table 2

#### Pulling-Grip Selection Table for Cables of Different Diameters to Be Pulled in One Grip

Grip Circumference R	ange	Cat. No. Size	Grip Diameter Range	
Fractional Inches	Decimal Inches	Code	Fractional Inches	Decimal Inches
25/32-1-11/64	.78–1.17	025	1/8–3/8	.12–.37
1-11/64-1-37/64	1.17–1.57	037	3/8-1/2	.37–.50
1-37/64-1-15/16	1.57-1.94	062	1/2-5/8	.50–.62
1-37/64-2-3/8	1.57-2.37	050	5/8-3/4	.62–.75
2-3/8-3-5/32	2.37-3.15	075	3/4–1	.75–1.00
3-5/32-3-15/16	3.15-3.94	100	1–1-1/4	1.00-1.25
3-15/16-4-23/32	3.94-4.72	125	1-1/4-1-1/2	1.25-1.50
4-23/32-5-33/64	4.72-5.51	150	1-1/2-1-3/4	1.50-1.75
5-33/64-6-19/64	5.51-6.29	175	1-3/4-2	1.75-2.00
6-19/64-7-55/64	6.29-7.86	200	2–2-1/2	2.00-2.50
7-55/64-9-7/16	7.86-9.43	250	2-1/2-3	2.50-3.00
9-7/16-11-1/64	9.43-11.01	300	3–3-1/2	3.00-3.50
11-1/64-12-37/64	11.01–12.58	350	3-1/2-4	3.50-4.00

<sup>&</sup>quot;Grip Circumference Range" refers to circumference of all cables held together.

- Determine grip circumference range by measuring circumference of bundle of cables to be held.
- 2. Read down to locate correct range.
- 3. Read across for catalog number size code.



#### **Example:**

For four cables together with circumference of 6.35", use grip containing catalog number size code "200".

#### Table 4

#### **Reference Table: AWG Wire Sizes**

For your convenience, the following are representative portable cord diameters.

				Cond	uctors			
AWG Wire Size & Type		2	;	3		4	!	5
	0	2	0	2	0	2	0	2
18 SO, STO	3.90	.390	.410	.405	.440	.435	.500	.495
18 SJ0, SJT0	.310	.300	.330	.330	.360	.360	_	_
16 SO, STO	.410	.405	.430	.430	.490	.485	.530	.525
16 SJ0, SJT0	.330	.330	.340	.360	.390	.390	_	_
14 SO, STO	.530	.530	.560	.560	.610	.605	.680	.685
12 SO, STO	.610	.605	.640	.640	.680	.670	.750	.730
10 SO, STO	.650	.640	.690	.695	.750	.820	.815	_
8 SO, STO	.810	.810	.910	.910	.990	.990	1.080	1.080
6 SO, STO	.930	.930	1.010	1.010	1.100	1.100	1.200	1.200

#### Table 3

#### Reference Table: Dimension Conversions for Ordering Tables

Decimal Inches	Fractional Inches	Metric Dimen- sions (mm)
0.12-0.24	1/8-15/64	3.17-5.95
0.25-0.36	1/4-23/64	6.35-9.13
0.37-0.49	3/8-31/64	9.52-12.30
0.50-0.61	1/2-39/64	12.70-15.48
0.62-0.74	5/8-47/64	15.88-18.65
0.75-0.99	3/4-63/64	19.05-25.00
1.00-1.24	1-1-15/64	25.40-31.35
1.25-1.49	1-1/4-1-31/64	31.75–37.70
1.50–1.99	1-1/2-1-63/64	38.10-50.40
2.00-2.49	2-2-31/64	50.80-63.10
2.50-2.99	2-1/2-2-63/64	63.50-75.80
3.00-3.49	3-3-31/64	76.20-88.50
3.50-3.99	3-1/2-3-63/64	88.90-101.20

#### Table 5

#### Reference Table: AWG or MCM Wire Sizes

This table is to be used as a guide only. Sizes may vary by manufacturer.

AWG	Dian	neter
OR MCM	TTHN	THW
14	.105	.162
12	.122	.179
10	.153	.199
8	.201	.259
6	.257	.323
4	.328	.372
3	.356	.401
2	.388	.433
1	.450	.508
1/0	.491	.549
2/0	.537	.595
3/0	.588	.647
4/0	.646	.705
250	.716	.788
300	.771	.843
350	.822	.895
400	.869	.942
500	.955	1.03
600	_	1.12
700	_	1.19
750	_	1.22
1000	_	1.38





## **Wire-Mesh Grips**

## Single-Weave, Flexible-Eye Pulling Grips



KPJ-50

		l l	(PJ Junior Duty			KPL Ligh	nt Duty	
					Short L	ength		
Cable Dia.*	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight
.50"61"	KPJ-50	8.5"	260 lbs. (118 kg)	.05 lbs.	l –	_	_	_
.75"99"	KPJ-75	10"	560 lbs. (254 kg)	.10 lbs.	_	_	_	_
1.00"-1.24"	KPJ-100	11.5"	780 lbs. (354 kg)	.28 lbs.	_	_	_	_
1.25"-1.49"	_	_	_	_	KPL-125-1	14"	1060 lbs. (481 kg)	.40 lbs.
1.50"-1.74"	_	_	_	_	KPL-150-1	15"	1360 lbs. (617 kg)	.40 lbs.
2.00"-2.49"	_	_	_	_	KPL-200-1	18"	1700 lbs. (771 kg)	.65 lbs.

<sup>\*</sup>For equivalent cable diameters in fractional inches and in metric dimensions (mm), see Dimensions Conversion Reference Table 3.

## **Double-Weave, Flexible-Eye Pulling Grips**



KPM-075

		KPM Med	lium Duty					KP Heav	y Duty			
						Short L	ength.			Medium L	Medium Length	
Cable Dia.*	Cat. No.	Loaded/ Compressed Mesh Length	Maximum Safe Load	Weight	Cat. No.	Loaded/ Compressed Mesh Length	Maximum Safe Load	Weight	Cat. No.	Loaded Compressed Mesh Length	Maximum Safe Load	Weight
.50"61"	KPM-050	13"	480 lbs. (218 kg)	.10 lbs.	_	_	_	_	_	_	_	_
.75"99"	KPM-075	16"	1030 lbs. (467 kg)	.20 lbs.	KP-075-24	24"	1360 lbs. (617 kg)	.50 lbs.	KP-075-36	36"	1360 lbs. (617 kg)	.74 lbs.
1.00"-1.37"	KPM-100	18"	1420 lbs. (644 kg)	.40 lbs.	_	_	_	_	_	_	_	_
1.00"-1.49"	-	_	_	_	KP-100-24	24"	1920 lbs. (871 kg)	1.1 lbs.	KP-100-36	36"	1920 lbs. (871 kg)	1.0 lbs.
1.50"-1.99"	-	_	_	_	_	_	_	_	KP-150-36	36"	3280 lbs. (1488 kg)	1.6 lbs.

<sup>\*</sup>For equivalent cable diameters in fractional inches and in metric dimensions (mm), see Dimensions Conversion Reference Table 3.

**AWARNING:** Do NOT exceed maximum safe load as listed on the label attached to the product.

**AWARNING:** Do NOT use on live circuits.

**AWARNING:** Always match proper size and type of grip to application.

 $\pmb{\hat{\mathbb{A}}} \textbf{WARNING:}$  Always inspect equipment before use.





## **Double-Weave, Rotating-Eye Pulling Grips**



KPS-062-1

				KPS I	leavy Duty				
		Medium	Length		Medium-Long Length				
Cable Dia.*	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight	
.50"61"	KPS-050-2	16"	1120 (508 kg)	.45 lbs.	<b> </b>	_	_	_	
.62"74"	KPS-062-2	16"	1360 (617 kg)	.50 lbs.	_	_	_	_	
.75"99"	KPS-075-2	20"	1360 (617 kg)	.85 lbs.	_	_	_	_	
1.00"-1.24"	KPS-100-2	20"	2560 (1161 kg)	1.9 lbs.	_	_	_	_	
1.00"-1.49"	<b>—</b>	_	_	_	KPS-100-3	33"	3280 (1488 kg)	2.4 lbs.	
1.25"-1.49"	KPS-125-2	21"	2560 (1161 kg)	1.9 lbs.	_	_	_	_	
1.50"-1.99"	KPS-150-2	25"	3280 (1488 kg)	2.2 lbs.	KPS-150-3	34"	3280 (1488 kg)	2.5 lbs.	
2.00"-2.49"	KPS-200-2	26"	5440 (2468 kg)	4.1 lbs.	KPS-200-3	36"	5440 (2468 kg)	4.7 lbs.	
2.50"-2.99"	KPS-250-2	28"	6600 (2994 kg)	5.3 lbs.	_	_	_	_	
3.00"-3.49"	KPS-300-2	30"	8200 (3720 kg)	6.1 lbs.	_	_	_	_	
3.50"-3.99"	KPS-350-2	32"	9600 (4355 kg)	6.8 lbs.	_	_	_	_	

<sup>\*</sup>For equivalent cable diameters in fractional inches and in metric dimensions (mm), see Dimensions Conversion Reference Table 3.

## **Slack-Pulling, Offset Flexible-Eye Pulling Grips**



KSCK Medium Duty – Standard Length			KSSK Medium Duty – Standard Length					
Cable Dia.*	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight	Cat. No.	Loaded/Compressed Mesh Length	Maximum Safe Load	Weight
.75"99"	-	_	_	_	KSSK-075-1	12"	500 lbs. (227 kg)	.30 lbs.
1.00"-1.24"	KSCK-100-1	15"	800 lbs. (363 kg)	.50 lbs.	KSSK-100-1	15"	700 lbs. (318 kg)	.25 lbs.
1.25"-1.49"	—	_	_	_	KSSK-125-1	16"	800 lbs. (363 kg)	.25 lbs.

<sup>\*</sup>For equivalent cable diameters in fractional inches and in metric dimensions (mm), see Dimensions Conversion Reference Table 3.



AWARNING: Do NOT exceed maximum safe load as listed on the label attached to the product.

**AWARNING:** Do NOT use on live circuits.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Always inspect equipment before use.



## **Construction Tools**

#### Tie-Wire Reel

- Rugged, lightweight reel is smooth aluminum alloy with wear parts made of steel.
- Feeds pre-coiled wire smoothly, easily and quickly to save time and reduce wasted wire.
- Designed for left- or right-hand use.
- Large, comfortable rewind knob.
- Easily-removed cover plate that permits quick, convenient reloading to handle all types of wire.

Cat. No.	Diameter	Width	Weight (lbs.)
27400	6-1/4" (159 mm)	2-25/32" (71 mm)	2.35



#### 27400

#### **Tie-Wire Accessories**

- Strong double-tongue buckle with keeper.
- Has separate reel-strap with its own buckle that lets you quickly and conveniently put on or take off a Klein tie-wire reel and optional pad without removing the belt or your tool pouch.
- Leather construction.
- Heavy-Duty Tie-Wire Belts.

Cat. No.	Waist Size	Belt Size Range	Width	Weight (lbs.)
5420S	36" (914 mm)	32" - 40" (813 mm - 1016 mm)	2" (51 mm)	.85
5420	40" (1016 mm)	36" - 44" (914 mm - 1118 mm)	2" (51 mm)	.95
5420L	44" (1118 mm)	40" – 48" (1016 mm – 1219 mm)	2" (51 mm)	1.05
5420XL	48" (1219 mm)	44" - 52" (1118 mm - 1321 mm)	2" (51 mm)	1.15

Tie-Wire Reel Pad.

Cat. No.	Length	Width	Weight (lbs.)
27450	7" (178 mm)	7" (178 mm)	.300





For more accesories information. see Tool Pouches, Carriers, Belts & Suspenders section

27450

#### **Rebar Hickeys**

 Lightweight rebar hickey has exceptionally durable steel-alloy head and extra-strong handle to withstand extreme conditions

64310

Cat. No.	Hickey Size	Bends Rebar Size	Head Type and Bending Angle	Handle Length	Weight (lbs.)
64309	1a	nos. 3 (.375" dia.), 4 (.500" dia.)	double 65° and 90°	24" (610 mm)	3.50
64310	2	no. 5 (.625" dia.)	single 65°	40" (1016 mm)	7.50
64311	3	no. 6 (.750" dia.)	single 65°	40" (1016 mm)	8.00
64312	4	nos. 7 (.875" dia.), 8 (1.00" dia.), 9 (1.128" dia.)	single 65°	60" (1524 mm)	16.40

## Grizzly® Bar





64306

- A heavy, strong, multi-purpose tool that saves time and effort on the job.
- The 3" (76 mm) width protects concrete when stripping forms.
- Efficient blade angle and 55-1/2" (141 cm) total length provide high leverage as a crow bar, as well as a nail and spike puller.
- Blade is forged and hardened alloy with keyhole nail-pulling slot in center and "V" notch in tapered edge.
- · Very efficient nail-pulling tool even in awkward positions.
- Can be used to help align walls during tilt-up construction, to roll and align large pipe, to remove shingles and flooring, and for many other stripping and prying tasks.

Cat. No.	Overall Length	Weight (lbs.)
64306	55-1/2" (1410 mm)	12.00

All dimensions are in inches and (millimeters).

For additional construction tools, see Mining Tools section

**AWARNING:** Always wear approved personal protective equipment.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT exceed rated capacity for rebar shear and rebar hickeys.



3242

3245

3252

3255

## **Connecting Bars**

#### **Hex Bars**

- Provides extra leverage when positioning steel members and aligning bolt holes.
- Forged fit-up bar is pointed on one end.
- Chisel-end is at a 15° angle to give greater leverage.

Cat. No.	Hex Diameter	Length	Weight (lbs.)
3242	3/4" (19 mm)	30" (762 mm)	3.50
3243	7/8" (22 mm)	36" (914 mm)	6.00
3244	3/4" (19 mm)	24" (610 mm)	2.50

Cat. No.	Hex Diameter	Length	Weight (lbs.)
Straight 0	hisel-End		
3240	3/4" (19 mm)	30" (762 mm)	3.80

#### **Round Bars**

- Provides extra leverage when positioning steel members and aligning bolt holes.
- Forged fit-up bar is pointed on one end.
- Chisel-end is at a 15° angle to give even greater leverage.

Cat. No.	Diameter	Length	Weight (lbs.)
3245	3/4" (19 mm)	30" (762 mm)	3.30
3246	7/8" (22 mm)	36" (914 mm)	5.50
3247	3/4" (19 mm)	24" (610 mm)	2.50


Cat. No.	Diameter	Length	Weight (lbs.)
3248	7/8" (22 mm)	30" (762 mm)	4.30
Straight C	hisel-End		
3241	3/4" (19 mm)	30" (762 mm)	3.20

## **Pins**

#### **Standard Bull Pins**

- Machined from quality alloy steel.
- Heat-treated for strength, black finish for rust resistance.

3251 1-1/16" (27 mm) 3/8" (10 mm) 15" (381 mm) 2.50 3252 1-3/16" (30 mm) 7/16" (11 mm) 15" (381 mm) 3.10 3257 1-1/16" (27 mm) 3/8" (10 mm) 12" (305 mm) 1.70	Cat. No.	Top Diameter	Point Diameter	Length	Weight (lbs.)
to the feeting the feeting to the feeting	3251	1-1/16" (27 mm)	3/8" (10 mm)	15" (381 mm)	2.50
3257 1-1/16" (27 mm) 3/8" (10 mm) 12" (305 mm) 1 70	3252	1-3/16" (30 mm)	7/16" (11 mm)	15" (381 mm)	3.10
0207 1 1710 (27 11111) 070 (10 11111) 12 (000 11111) 1370	3257	1-1/16" (27 mm)	3/8" (10 mm)	12" (305 mm)	1.70



Note: OSHA 1926.301 (c) specifically states: "Impact tools, such as drift pins, wedges and chisels, shall be kept free of mushroomed heads."

#### **Broad Head Bull Pins**

- Forged, heat-treated bull pin increases efficiency by providing a larger striking surface.
- Angled head and smooth blending of radii increase strength and reduce the danger of chipping.
- Below the head, squared-off shoulders have been forged to provide a surface for applying wrench to loosen wedged bull pins.
- Long, even taper reduces binding and hang-up.
- Added resistance to "mushrooming" permitting much longer use than is possible with conventional designs.



Cat. No.	lop Diameter	Point Diameter	Length	Weight (lbs.)
3255	1-1/4" (32 mm)	5/16" (8 mm)	13-3/4" (349 mm)	2.90
3256	1-1/16" (27 mm)	1/4" (6 mm)	10" (254 mm)	1.60

Note: OSHA 1926.301 (c) specifically states: "Impact tools, such as drift pins, wedges and chisels, shall be kept free of mushroomed heads."

## **Barrel-Type Drift Pins**

- Machined from quality alloy steel.
- Tapers are uniform and blend into body diameter.
- Tough, drop-forged steel will properly end-pein in use.
- · Heat-treated for strength.
- Black finish for rust resistance.



8" (203 mm)

1.50

9/16" (14 mm)

All dimensions are in inches and (millimeters).

For additional construction tools, see Mining Tools section

3263

**AWARNING:** Always wear approved eye protection.

1-1/16" (27 mm)



257

## **Construction Wrenches**

#### **Adjustable-Head Construction Wrenches**

- Eliminates the need to carry several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle.
- Industrial black finish fo r corrosion resistance.
- Lanyard hole for easy tool tethering.



Cat. No.	Max. Size Capacity	Length	Weight (lbs.)
3239	1-1/2" (38 mm)	16" (406 mm)	2.30
3227	1-5/16" (33 mm)	11" (279 mm)	1.20

## 1/2"- Drive Ratcheting Construction Wrench


- Accepts 1/2" square-drive hex socket.
- · Reversible ratchet.
- Eliminates the need for carrying several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle for aligning bolt and/or rivet holes.
- Industrial black finish for corrosion resistance.

Cat. No.	Overall Length	Weight (lbs.)
3238	15" (381 mm)	2 10

#### **Erection Wrenches**

- Forged from select alloy steel to withstand high-leverage and heavy loads.
- Extra-heavy-duty head area gives maximum strength and durability.
- Continuous taper of handle makes lining-up bolt holes easy and works on a range of bolt-hole sizes without binding.
- Extra-large hub area works on larger diameter holes better than other wrenches.
- Catalog number, bolt size and nominal opening size are stamped on every wrench for easy identification.
- American Bridge design.

Cat. No.	Nut Type	Bolt Size	Nom. Opening	Head Width	Taper Diameter	Overall Length	Weight (lbs.)
3210	U.S. heavy	1/2"	7/8"	2-1/4"	7/8" to 3/16"	14-3/4"	1.36
3211	U.S. heavy	5/8"	1-1/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3212	U.S. heavy	3/4"	1-1/4"	2-1/2"	1" to 1/4"	16-5/8"	1.98
3213	U.S. heavy	7/8"	1-7/16"	3"	1-1/8" to 9/32"	17-3/8"	2.72
3214	U.S. heavy	1"	1-5/8"	3-5/8"	1-1/8" to 1/4"	18"	3.36
3219	U.S. regular	1/2"	3/4"	2-1/4"	7/8" to 8/16"	14-3/4"	1.36
3220	U.S. regular	1/2"	13/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.35
3221	U.S. regular	5/8"	1"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3222	U.S. regular	3/4"	1-1/8"	2-1/2"	1" to 1/4"	16-5/8"	2.00
3223	U.S. regular	7/8"	1-5/16"	3"	1-1/8" to 9/32"	17-3/8"	2.87
3224	U.S. regular	1"	1-1/2"	3-5/8"	1-1/8" to 1/4"	18"	3.37
3231	utility	5/8"	15/16"	2-1/4"	7/8" to 3/16"	14-3/4"	1.31
3232	utility	3/4"	1-1/16"	2-1/2"	1" to 1/4"	16-5/8"	2.00



3238

3231

- B Head Width
- C Overall Length

#### For additional construction tools, see Mining Tools section

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT push or hammer wrench.

AWARNING: Do NOT extend handle length.



258

## Bars - Construction

### Crowbars - Hexagon (St. Angelo Bars)



5CB180025

5CBR180030

5GNB180030




- Forged from tough high-tensile carbon manganese steel.
- Ground and sharpened to a diamond point for easier digging and breaking concrete.
- Long tapered blade also for easier digging.
- Both ends heat treated for increased performance and strength.
- Hexagon bar profile for greater control.
- Anti-corrosive primer with enamel finish.
- Precision heat treated to best suit product application.



Cat No	Blade Width	Hexagon Diameter	Length	Weight
5CB150025	2" (50 mm)	1" (25 mm)	59" (1500 mm)	13.49 lbs. (6.12 kg)
5CB150030	2" (50 mm)	1-3/16" (30 mm)	59" (1500 mm)	18.95 lbs. (8.60 kg)
5CB165025	2" (50 mm)	1" (25 mm)	65" (1650 mm)	14.77 lbs. (6.70 kg)
5CB165030	2" (50 mm)	1-3/16" (30 mm)	65" (1650 mm)	20.94 lbs. (9.50 kg)
5CB180025	2" (50 mm)	1" (25 mm)	71" (1800 mm)	16.20 lbs. (7.35 kg)
5CB180030	2" (50 mm)	1-3/16" (30 mm)	71" (1800 mm)	23.03 lbs. (10.45 kg)

#### Crowbars - Round (St. Angelo Bars)



• Forged from tough high-tensile carbon manganese steel.

Ground and sharpened to a diamond point for easier digging and breaking concrete.

- Long, tapered blade also for easier digging.
- Both ends heat treated for increased performance and strength.
- Round bar profile easier on hands.
- Anti-corrosive primer with enamel finish.
- Precision heat treated to best suit product application.

Cat. No.	Blade Width	Diameter	Length	Weight
5CBR180022	1-1/2" (38 mm)	7/8" (22 mm)	71" (1800 mm)	12.12 lbs. (5.50 kg)
5CBR180025	2" (50 mm)	1-1/16" (27 mm)	71" (1800 mm)	17.08 lbs. (7.75 kg)
5CBR180030	2" (50 mm)	1-3/16" (30 mm)	71" (1800 mm)	21.38 lbs. (9.70 kg)

## Gooseneck Bar - Hexagon

- Used for levering and moving objects into place with a lift and swivel motion.
- Forged from tough high-tensile carbon manganese steel.
- Diamond point and gooseneck ends for flexibility of use.
- Gooseneck set for improved leverage.
- Hexagon bar profile for greater control.
- Precision heat treated to best suit product application.

Cat. No.	Hexagon Diameter	Length	Weight
5GNB180030	1-3/16" (30 mm)	71" (1800 mm)	24.74 lbs. (11.10 kg)





All dimensions are in inches and (millimeters).

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eve protection and gloves.

## **Bars - Construction**

#### Slate Bars – Hexagon (Pinch Bars)



5PB180025



- Forged from high-tensile carbon manganese steel for maximum strength.
- Heel offset to 40° angle for optimum lifting.
- Hexagon bar profile gives greater control and reduces bar roll.
- Heat-treated blade ends for maximum toughness.
- Precision heat treated to best suit product application.




Cat. No.	Hexagon Diameter	Length	Weight	
5PB150025	1" (25 mm)	59" (1500 mm)	13.55 lbs. (6.15 kg)	
5PB150030	1-3/16" (30 mm)	59" (1500 mm)	19.62 lbs. (8.90 kg)	
5PB165025	1" (25 mm)	65" (1650 mm)	15.01 lbs. (6.81 kg)	
5PB165030	1-3/16" (30 mm)	65" (1650 mm)	21.91 lbs. (9.94 kg)	
5PB180025	1" (25 mm)	71" (1800 mm)	16.82 lbs. (7.63 kg)	
5PB180030	1-3/16" (30 mm)	71" (1800 mm)	24.31 lbs. (11.02 kg)	
5PB45016	5/8" (16 mm)	18" (450 mm)	1.58 lbs. (0.72 kg)	
5PB60020	25/32" (20 mm)	24" (600 mm)	3.37 lbs. (1.53 kg)	
5PB60025	1" (25 mm)	24" (600 mm)	5.31 lbs. (2.41 kg)	
5PB75025	1" (25 mm)	30" (750 mm)	6.70 lbs. (3.04 kg)	
5PB90025	1" (25 mm)	36" (900 mm)	8.04 lbs. (3.65 kg)	

#### Scaling Bars - Tubular Aluminum (Aluminium) - Hexagon

7SCTH1800

- Used in the mining industry for prying overhanging rock.
- Aluminium tube body for light weight and less user fatigue.
- Inserted steel ends forged from tough carbon manganese steel.
- Heel offset to 40° angle for optimum levering.
- Precision heat treated to best suit product application.
- Hexagon shape for increased control.



## Scaling Bars - Tubular Aluminum (Aluminium) - Round



- Used in the mining industry for prying overhanging rock.
- Aluminium tube body for light weight and less user fatigue.
- Inserted steel ends forged from tough carbon manganese steel.
- Heel offset to 40° angle for optimum levering.
- Precision heat treated to best suit product application.

Cat. No.	Diameter	Length	Weight
7SCT1800	1-1/4" (32 mm)	71" (1800 mm)	6.37 lbs. (2.89 kg)
7SCT3660	1-1/4" (32 mm)	144" (3660 mm)	9.25 lbs. (4.20 kg)
7SCT4320	1-1/4" (32 mm)	170" (4320 mm)	10.20 lbs. (4.63 kg)

All dimensions are in inches and (millimeters).

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection and gloves.





## Bars - Mining

## Scaling Bars - Chrome Alloy Steel - Hexagon



7SC150019



- Forged from chrome alloy steel.
- Heat-treated blades for maximum toughness.
- Hex profile for good control.
- Heel offset to 40° angle for optimum levering.
- Precision heat treated to best suit product application.



Cat. No.	Hexagon Diameter	Length	Weight
7SC120019	25/32" (20 mm)	47" (1200 mm)	6.87 lbs. (3.12 kg)
7SC150019	25/32" (20 mm)	59" (1500 mm)	8.62 lbs. (3.91 kg)
7SC180019	25/32" (20 mm)	71" (1800 mm)	10.31 lbs. (4.68 kg)
7SC210019	25/32" (20 mm)	83" (2100 mm)	12.01 lbs. (5.45 kg)
7SC240019	25/32" (20 mm)	94-1/2" (2400 mm)	13.75 lbs. (6.24 kg)

## **Chisels & Punches**

#### Cold Chisels - Alloy Cross Cut

- Used for removing oil seals.
- Also used for cutting in corners and difficult or confined areas.
- Forged from chrome alloy steel to give a harder blade with great resilience.
- Precision hardened and tempered so blade will not shatter when struck hard.
- Accurately ground to the optimum angle for cutting.



7CHC15013

Cat. No.	Blade Width	Overall Length	Weight	
7CHC15013	1/4" (6.5 mm)	6" (150 mm)	0.26 lbs. (0.12 kg)	
7CHC17516	5/16" (8 mm)	7" (175 mm)	0.50 lbs. (0.23 kg)	
7CHC20020	3/8" (10 mm)	8" (200 mm)	0.55 lbs.(0.25 kg)	

#### **Brass Punches**

- Used where a softer punch is needed, e.g. where damage may occur from using a hardened punch.
- Selected brass, correct composition for punch use.
- Knurled handle for gripping easily.
- Chamfered head for safety.



4BP16

Cat. No.	Diameter	Overall Length	Weight
4BP10	3/8" (10 mm)	6" (150 mm)	0.22 lbs. (0.10 kg)
4BP12	1/2" (12 mm)	7" (175 mm)	0.30 lbs. (0.14 kg)
4BP16	5/8" (16 mm)	7" (175 mm)	0.66 lbs. (0.30 kg)
4BP19	3/4" (19 mm)	8" (200 mm)	1.05 lbs. (0.48 kg)
4BP25	1" (25 mm)	8" (200 mm)	1.87 lbs. (0.85 kg)
4BPSET5	3/8", 1/2", 5/8", 3/4", 1" (10 mm, 12 mm, 16 mm, 19 mm, 25 mm)	6", 7", 7", 8", 8" (150 mm, 175 mm, 175 mm, 200 mm, 200 mm)	4.38 lbs. (1.99 kg)
7BP29219	3/4" (19 mm)	11-1/2" (292 mm)	1.54 lbs. (0.70 kg)
7BP29225	1" (25 mm)	11-1/2" (292 mm)	2.75 lbs. (1.25 kg)
7BP29232	1-1/4" (32 mm)	11-1/2" (292 mm)	4.32 lbs. (1.96 kg)

262

## **Construction Tools**

#### **Barrel Drifts**

- Used for aligning holes in construction.
- Also used for expanding holes in mild steel.
- Forged from tough high-tensile steel.
- Taper is forged, not turned, for finer grain, giving greater tensile strength.
- Will not score edge when driven hard.
- Precision heat treated to best suit product application.



5BD24

Cat. No.	Point Diameter (approx.)	Diameter	Overall Length	Weight
5BD30	37/64" (14.5 mm)	1-3/16" (30 mm)	7-7/8" (200 mm)	1.76 lbs. (0.80 kg)
5BD33	5/8" (16 mm)	1-19/64" (33 mm)	7-7/8" (200 mm)	2.29 lbs. (1.04 kg)

#### **Podger Pins (Broad Head Bull Pins)**



- Used for aligning holes and expanding holes in mild steel.
- Forged from tough high-tensile carbon manganese steel.
- Forged, not turned, long tapered point for ease of aligning.
- For added safety, forged head prevents pin being driven right through hole and falling.
- Hex shaft allows spanner to be used to assist removal.
- · Can be carried on belt.
- Precision heat treated to best suit product application.

Cat. No.	Point	Diameter Across Hexagon Points	Hexagon Shaft Diameter	Overall Length	Weight
5P0P25	1/2" (12 mm)	1-3/32" (28 mm)	1" (25 mm)	16" (400 mm)	3.26 lbs. (1.48 kg)
5P0P30	9/16" (14.5 mm)	1-5/16" (33.5 mm)	1-3/16" (30 mm)	16" (400 mm)	4.49 lbs. (2.04 kg)

## Fox Wedge - Stainless Steel

- Used for splitting mating surfaces and for packing machinery and structures before fixing.
- Also used in the marine environment because of its corrosion-resistant properties.
- Forged from stainless steel for greater hardness and non-magnetic properties.
- Ground blade with fine edge for easy entry.
- Precision heat treated to best suit product application.



7FWSS10025

Cat. No.	Width	Thickness	Overall Length	Weight
7FWSS10025	1" (25 mm)	5/16" (8 mm)	4" (100 mm)	0.22 lbs (0.10 kg)

All dimensions are in inches and (millimeters).

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection and gloves.





## **Construction Tools**

#### **Pry Bar**





- Used for prying, separating flanges and aligning holes.
- Forged from tough high-tensile carbon manganese steel.
- Thin, finely ground curved chisel end for ease of entry between surfaces.
- Forged, not turned, long tapered point for maximum strength.
- Hexagon profile for greater control.
- Precision heat treated to best suit product application.

Cat. No.	Chisel Width	Hexagon Diameter	Overall Length	Weight
5PRBP45016	25/32" (20 mm)	5/8" (16 mm)	18" (450 mm)	1.67 lbs. (0.76 kg)

## Pinch Bars - Hexagon (Podger Bars)



5P0B37520

- Used for levering and aligning.
- Forged from tough high-tensile carbon manganese steel.
- Heel set to 40° angle for optimum levering; blade ground to 30° angle for easy entry between surfaces.
- Taper is forged, not turned, for finer grain, giving greater tensile strength.
- Hexagon profile for greater control and to minimize bar roll.
- Precision heat treated to best suit product application.

Cat. No.	Point Diameter	Hexagon Diameter	Overall Length	Weight
5P0B37516	5/16" (8 mm)	5/8" (16 mm)	15" (375 mm)	1.21 lbs. (0.55 kg)
5P0B37520	3/8" (10 mm)	25/32" (20 mm)	15" (375 mm)	1.82 lbs. (0.83 kg)
5P0B45016	5/16" (8 mm)	5/8" (16 mm)	18" (450 mm)	1.49 lbs. (0.68 kg)
5P0B45020	3/8" (10 mm)	25/32" (20 mm)	18" (450 mm)	2.27 lbs. (1.03 kg)
5P0B60020	3/8" (10 mm)	25/32" (20 mm)	24" (600 mm)	3.15 lbs. (1.43 kg)
5P0B90020	3/8" (10 mm)	25/32" (20 mm)	36" (900 mm)	4.85 lbs. (2.20 kg)



265

## **Construction Tools**




- Used for driving in star (fencing) droppers.
- Also used to drive in marker pegs, stakes and concreting stakes.
- Heavy unit drives droppers very quickly and efficiently.
- Solid steel handles and slug are welded together, which gives greater strength.

Cat. No.	Internal Diameter	Overall Length	Weight
5SDSH	2-1/8" (54 mm)	33-55/64" (860 mm)	19.13 lbs. (8.68 kg)

## **Star Dropper Remover**

- Used for removing star droppers (also called star pickets or fencing droppers).
- Also used for removing selected pipes and steel pegs.
- Gripper made from high-tensile steel for durability and long life.
- Gripper bites efficiently into dropper for easy extraction.

	e for excellent lever	age.					
Cat. No.	Handle Length	Slot Opening	Overall Height	Weight		- MR	
5SDR	36" (900 mm)	1-21/64" x 2" (34 x 50 mm)	32* (800 mm)	17.76 lbs. (8.06 kg)		A	
							5SDR
						-	



## Hammers

#### Drill Hammer -**Wooden Handle**

- Used for mining and confined environments.
- Also ideal for close work with enough head weight for effective hammering.
- Head forged from high-tensile carbon manganese steel, with hardened and tempered face and claw.
- Fitted with tough Australian spotted gum hardwood handle, oiled for long life and user comfort.
- Handle is fitted to head with a glued wooden and steel wedge assembly.
- Precision heat treated to best suit product application.
- This product must be maintained in accordance with Australian standard AS 3797:1991.

at. No. Head Weight		Overall Length	Weight
5HDRH2.0	4.4 lbs. (2.0 kg)	16" (400 mm)	4.8 lbs. (2.18 kg)

## Mason's Club Hammer -**Wooden Handle**

- Great all-around club hammer for general striking applications.
- Forged from tough high-tensile carbon manganese steel, with hardened and tempered face and claw.
- Fitted with tough Australian spotted gum hardwood handle, oiled for long life and user comfort.
- Ideal for work in confined spaces.
- Handle is fitted to head with a glued wooden and steel wedge assembly.
- Precision heat treated to best suit product application.
- This product must be maintained in accordance with Australian standard AS 3797:1991.

Cat. No.	Head Weight	Overall Length	Weight
5HCMH1.35	3 lbs. (1.35 kg)	10" (250 mm)	3.54 lbs. (1.61 kg)

## Brass Sledge Hammers - Fiberglass Rubber Grip Handle



- Used in non-sparking environments or to avoid damage to struck objects.
- · Head forged from brass for softer, non-damaging blow.
- Head is pinned to handle as well as epoxied to prevent head coming off.
- Comfortable, thick rubber grip handle for increased protection from shock and vibration.
- Handle includes both overstrike protection and large sweep at base to prevent loss of grip. This product must be maintained in accordance with Australian standard AS 3797:1991.

Cat. No.	Head Weight	Overall Length	Weigh

Cat. No.	Head Weight	Overall Length	Weight
7HBRFRH04	4 lbs. (1.81 kg)	16" (400 mm)	4.89 lbs. (2.22 kg)
7HBRFRH07	7 lbs. (3.17 kg)	32" (800 mm)	9.87 lbs. (4.48 kg)
7HBRFRH10	10 lbs. (4.53 kg)	36" (900 mm)	12.23 lbs. (5.55 kg)
7HBRFRH14	14 lbs. (6.35 kg)	36" (900 mm)	16.73 lbs. (7.59 kg)





266



## **Hammers**

## Chipping Hammer - Rubber Grip

- Used for chipping off slag and spatter around welds.
- Also used as geologists' or miners' tool.
- Head forged from chrome alloy steel and hardened and tempered for maximum toughness.
- Ground and sharpened vertical chisel and diamond point.
- Excellent balance with hardened ends that do not flatten when chipping.
- Precision heat treated to best suit product application.



Cat. No.	Head Length	Overall Length	Weight
5WHRG	6-11/16" (170 mm)	10-15/64" (260 mm)	1.14 lbs. (0.52 kg)

## **Safety Punches**

#### **Hand Saver Punch**



- Used to safely drive out pins and keys in machinery.
- Long, two-handed rubber handle to lessen shocks from blows.
- Head attached with wire rope to reduce shock.
- Urethane ring around head to reduce likelihood of chipping.
- · Heat-treated punch, so it will not shatter.

Cat. No.	Diameter	Shaft Length	Weight (lbs.)	
7WRP13	1/2" (13 mm)	4-3/4" (120 mm)	2.98 (1.35 kg)	
7WRP16	5/8" (16 mm)	4-3/4" (120 mm)	3.20 (1.45 kg)	
7WRP19	3/4" (19 mm)	4-3/4" (120 mm)	3.64 (1.65 kg)	
7WRP22	7/8" (22 mm)	4-3/4" (120 mm)	4.41 (2.00 kg)	
7WRP25	1" (25 mm)	4-3/4" (120 mm)	4.63 (2.10 kg)	
7WRP32	1-1/4" (32 mm)	4-3/4" (120 mm)	5.29 (2.40 kg)	

All dimensions are in inches and (millimeters).

#### **AWARNING:**

Strike squarely - avoid glancing blows. Always ensure that you and persons in the vicinity wear approved eye protection and gloves.

#### AWARNING:

This tool can be made to chip if struck against another tool or other hard object, resulting in possible eye or other injury.





## **Tyre (Tire) Products**

## Tyre (Tire) Lever





5TL600

- Used for removal and fitting of 4WD car and truck tires.
- Forged from tough chrome alloy steel.
- · Precision hardened and tempered to be tough and resilient.
- Fine tapered and ground ends for easier use and prevention of damage to tires.

Cat. No.	Thickness	Width	Overall Length	Weight
5TL600	27/64" (10.8 mm)	1-7/64" (28 mm)	24 -1/2" (620 mm)	2.51 lbs. (1.14 kg)



#### **AWARNING:**

Strike squarely - avoid glancing blows. Always ensure that you and persons in the vicinity wear approved eye protection and gloves.

#### AWARNING:

This tool can be made to chip if struck against another tool or other hard object, resulting in possible eye or other injury.





## **Cutting & Notching Tools - Journeyman™ Snips**

JOURNEYMAN

Features



#### **Aviation Snips**

#### Additional Features:

 J1100L, J1101R, J1102S Journeyman snips cut 18 gauge cold rolled steel and 22 gauge stainless steel.

 J2103S Journeyman Bulldog snips cut 16 gauge cold rolled steel and 18 gauge stainless steel.





Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity: Cold Rolled/Stainless Steel	Weight (oz.)
J1100L	left/straight	aviation	1-3/8" (35 mm)	red/black	9-7/8" (250 mm)	18 gauge/22 gauge	14.4
J1101R	right/straight	aviation	1-3/8" (35 mm)	green/black	9-7/8" (250 mm)	18 gauge/22 gauge	14.7
J1102S	straight/wide curves	aviation	1-1/2" (38 mm)	yellow/black	10-1/16" (255 mm)	18 gauge/22 gauge	14.4
J2103S	notch/straight	bulldog	7/8" (22 mm)	yellow/black	9-7/16" (240 mm)	16 gauge/18 gauge	13.9

## **Right Angle Snips**

#### Additional Features:

- J2104L, J2105R Journeyman snips cut straight, curves, and tight circles in 24 gauge cold rolled steel and 28 gauge stainless steel.
- Makes cutting easier in confined spaces (in ductwork, reaching through openings or against a wall).

Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity: Cold Rolled/Stainless Steel	Weight (oz.)
J2104L	left curves/tight circles/straight	right angle	1-1/4" (32 mm)	red/ black	7-15/16" (201 mm)	24 gauge/28 gauge	14.4
J2105R	right curves/tight circles/straight	right angle	1-1/4" (32 mm)	green/ black	7-15/16" (201 mm)	24 gauge/28 gauge	14.4

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

J2105R

J2104L

270

#### **Offset Snips**

#### Additional Features:

- J2100L, J2101R, J2102S and J2106S snips feature exclusive Klein Kurve<sup>®</sup> handles for natural hand positioning and ease of use.
- J2106S Journeyman snips cut 20 gauge cold rolled steel and 24 gauge stainless steel, with a 2-3/8" length of cut for faster cutting.
- J2100L, J2101R and J2102S Journeyman snips cut 18 gauge cold rolled steel and 22 gauge stainless steel.





Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity: Cold Rolled/Stainless Steel	Weight (oz.)
J2100L	left/straight	offset	1-1/4" (32 mm)	red/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.5
J2101R	right/straight	offset	1-1/4" (32 mm)	green/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.7
J2102S	straight/wide curves	offset	1-1/2" (38 mm)	yellow/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.5
J2106S	straight/wide curves	long cut offset	2-3/8" (60 mm)	yellow/black	10-1/2" (266 mm)	20 gauge/24 gauge	18.2

## **Cutting & Notching Tools**

## Aviation Snips - Regular/Offset/Bulldog

- Forged and heat-treated steel blades for strength and durability.
- Regular and offset blades have the capacity of cutting 18 gauge cold-rolled sheet metal and 22 gauge stainless steel sheet metal.
- Offset blades provide ease of cutting tight curves and keep user's hand away from metal.
- Bulldog snips (Cat. No. 2103) for notching or trimming 16 gauge cold-rolled sheet metal and 18 gauge stainless steel sheet metal.
- Spring-loaded for self-opening action.
- Latch keeps jaws closed when not in use.
- Hardened handles for extra strength.
- Contoured plastic handles are comfortable and color-coded by cutting pattern.



0+	$\cap \cap I$
	IUUI

Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity	Weight (oz.)
1100L	left / straight	aviation	1-3/8" (35 mm)	red	9-3/4" (248 mm)	18 ga.	14.4
1101R	right / straight	aviation	1-3/8" (35 mm)	green	9-3/4" (248 mm)	18 ga.	14.7
1102S	straight / wide curve	aviation	1-1/2" (38 mm)	yellow	10-1/8" (257 mm)	18 ga.	14.4
2100L	left / straight	offset	1-1/4" (32 mm)	red	9-1/2" (241 mm)	18 ga.	15.5
2101R	right / straight	offset	1-1/4" (32 mm)	green	9-1/2" (241 mm)	18 ga.	15.7
2102S	straight / wide curve	offset	1-1/2" (38 mm)	yellow	9-1/2" (241 mm)	18 ga.	15.5
2103	notch	bulldog	7/8" (22 mm)	yellow	9-1/4" (235 mm)	16 ga.	13.9

Repl	Replacement springs for aviation snips				
P406	replacement spring for Cat. Nos. 1100L and 1102S				
P407	replacement spring for Cat. No. 1101R				

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.





## **Cutting & Notching Tools**

## **Snap Lock Punch** Compound-leverage mechanism for greater control and easy operation. Drop-forged, steel jaw easily punches 3/8" (9.5 mm) wide impressions on metal edges to easily join pieces of sheet metal, duct, or pipe.

All-steel construction and nickel-chrome plated hardware provide long life and durability.

Vinyl grips with handle stops for added comfort and easy operation.

Cat. No.	Overall Length	Handle Color	Weight (lbs.)
86560	8" (203 mm)	blue	1.0




 6° angled, hollow-ground cutting edge for cutting full 3-1/2" (89 mm) straight cuts and wide curves.

- Easily replaceable cutting blades made of high-carbon steel.
- Cutting capacity: 22 gauge cold-rolled sheet metal; 26 gauge stainless steel sheet metal. Do not use to cut hardened wire, nails, or any other rounded surface.
- Lightweight magnesium handles.

Overall Length	Handle Color	Weight (oz.)			
13" (330 mm)	gray	13.4			
Replacement Parts					
3101 replacement blades for Cat. No. 3100					
	13" (330 mm) ent Parts	13" (330 mm) gray			

## **Seaming & Folding Tools**

#### **Hand Notcher**



- Drop-forged, high-impact steel jaw with 13/16" (21 mm) maximum throat depth.
- Jaws' hook design allows easy notching of corners and take-off tabs without slippage.
- All steel construction with nickel-plate and black-oxide finish provides long life and durability.
- Hardened steel handles include hand guards and are covered with vinyl grips for added comfort and easy operation.

Cat. No.	Overall Length	Handle Color	Weight (lbs.)
86551	8-1/2" (216 mm)	blue	1.0

#### **Nibbler Tool**

86560

- Cuts soft sheet metal, plastic, soft copper and aluminum, and tubing.
- Ideal for air conditioning and heating installation, automobile work. model making, and sheet metal construction.
- 1/4" cutting kerf.

Cat.

	Weight (oz.)	
per	5.6	

76011B

86551

18 gauge soft sheet metal, soft copper and aluminum up to 1/16", and tubing nibbler cutter 76011B with blade from a 1" I.D. Replacement Parts

**Cuts Up to** 

## replacement blade for Cat. No. 76011B

Description

## Seamers – Straight and Offset


- Compound-leverage mechanism easily and accurately bends, seams, and flattens sheet metal and non-ferrous metals.
- Jaw marked in 1/4" (6 mm) increments for precise bending measurements.
- All-steel construction and nickel-chrome plated hardware provide long life and durability.
- Vinyl grips with handle stops for added comfort and easy operation.
- Straight-handle model is used for most general applications.
- Offset-handle model (not pictured) is for use in overhead or confined areas .
- Broader jaw model for forming wider folds.
- Folds 22 gauge CRSM and 24 gauge SSSM.

Cat. No.	Туре	Jaw Size	Overall Length	Handle Color	Weight (lbs.)
86553	straight-hand seamer	3"	8-3/8" (213 mm)	blue	1.45
86552	offset-hand seamer	3"	8" (203 mm)	blue	1.46
86556	straight-hand seamer	6"	8-3/8" (213 mm)	blue	1.87



All dimensions are in inches and (millimeters).

AWARNING: Always wear approved eye protection.





## **Seaming & Folding Tools**

## Seamer Tongs, Straight and Offset

- Hot-drop forged for strength.
- Bending depth indicators marked in 1/4" (6 mm) increments.
- Cushioned handles.
- Offset-handle model for greater power and easy use in overhead and confined areas.

Cat. No.	Туре	Jaw Size	Overall Length	Bends	Handle Color	Weight (lbs.)
86554	offset	3"	9-3/4" (248 mm)	22 ga. CRSM	red	1.8
86555	straight	3"	9-3/4" (248 mm)	22 ga. CRSM	red	1.8



## **Tube Benders**

#### **Swivel Handle Tube Bender**

- Swivel handle repositions midway through bend to gain control, reduce efforts, and prevent handles from crossing
- Easily fabricates bends up to 180°.
- Calibrated to show angle of bend.

Cat. No.	Closed Overall Length	Tube O.D.	Weight (lbs.)
8900-3/8	14-1/4" (362 mm)	3/8"	1.75
8900-1/2	21-7/8" (556 mm)	1/2"	3.50



8900-1/2

#### **Professional 4-in-1 Tube Bender**



89030

- Bends four popular tube sizes.
- Calibrated markings for accurate left-hand, right-hand, and offset bends up to 90°.
- For soft copper, aluminum, and steel tubing.
- Bends 3/16", 1/4", 5/16" and 3/8" (6 mm and 8 mm) 0.D. tubing.

Cat. No.	Closed Overall Length	Weight (lbs.)
89030	10" (254 mm)	1.0

#### **Folding Tools**



88980

89019

- Two folding depths: 3/8" (10 mm) and 1" (25 mm).
- Handy sight gauges for accurate depth alignment.
- Made of heavy-duty 16 gauge steel for folding strength.

Cat. No.	Overall Length	Folds	Weight (lbs.)
88980	12" (305 mm)	24 ga. CRSM and 28 ga. SSSM	1.3
88981	18" (457 mm)	24 ga. CRSM and 28 ga. SSSM	2.0
88982	24" (610 mm)	24 ga. CRSM and 28 ga. SSSM	2.6

## **Spring Type Tube Bender Sets**

- 8-Pc. Set: Bends 1/4" to 7/8" O.D. tubing. 3-Pc. Set: Bends 1/4" to 3/8" O.D. tubing.
- Easily allows hand bending of soft copper and aluminum tubing into any shape without collapsing walls.
- Belled end for quick tube removal.

Cat. No.	Туре	Overall Length	Weight (oz.)
89018	8 pc. set	10" (254 mm) - 12" (305 mm)	50.75
89019	3 pc. set	10" (254 mm)	10

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.





# HVAC



## **Tube Cutters**

#### **Professional Tube Cutter**



88904

- Accurate 4 roller tracking system no spiraling.
- Professional reaming tool.
- Extra cutting wheel included in handle.

Cat. No.	Overall Length	Cuts	Weight (lbs.)
88904	6-1/32" (153 mm)	1/8" – 1-1/8" steel and copper tubing	1.31
Replace	ment Parts		
88905	replacement wheel	for Cat. No. 88904	.08

#### **Professional Tube Cutter**





88975

88976

- Smooth feed mechanism for precise, right angle cutting action.
- Includes retractable reamer with filing surface and spare cutter wheel.
- Not designed for cutting stainless steel or hard tempered tubing.

Cat. No.	Overall Length	Cuts	Weight (oz.)			
88975	5" (127 mm)	1/8" - 1-1/8" O.D. tubing	9.5			
Replacement Parts						
88976	replacement wheels + screw for Cat. No. 88975					

## **Swaging Tool – Punch Type**

#### **Professional 6-in-1 Swaging Punch**



- Swages six sizes of tubing.
- Hex design for ease of extraction.

66400

- Precision machined surface for ease of forming.
- High-alloy steel, heat-treated for strength and durability.

Cat. No.	Overall Length	Swages	Weight (oz.)
66400	5-3/16" (132 mm)	3/16", 1/4", 5/16", 3/8" 1/2", 5/8" O.D. tubing	5.92

#### **Professional Mini Tube Cutter**





88977

- Perfect for tight space cutting.
   Requires only 1-3/8" swing radius.
- Smooth feed mechanism for precise, right angle cutting action.
- Not designed for cutting stainless steel or hard tempered tubing.

Cat. No.	Overall Length	Cuts	Weight (oz.)			
88977	1-3/4" (44 mm)	1/8"-5/8" O.D. tubing	2.5			
Replacement Parts						
88978	replacement wheels + screw for Cat. No. 88977					

## **Tube Cutter Accessories**

## Inner-Outer Reaming and Deburring Tool

- Reams inside and outside edges of tubing.
- Deburrs with clockwise and counter-clockwise rotations.
- Reams copper, aluminum, PVC, and brass tubing.

Cat. I

89025



Vo.	Overall Length	Color	Reams	Weight (oz.)
	2-1/4" (57 mm)	yellow	3/16" to 1-1/2"	10.08

## **Tube Flaring & Swaging Tools**

## 45° Flaring and Swaging Tool Sets



- Self-centering, slip-on forged steel yoke easily forms quality flares/swages.
- Flares 1/8", 3/16", 1/4", 5/16", 3/8", 7/16", 1/2", 5/8" and 3/4" 0.D.
- Swages 3/16", 1/4", 5/16", 3/8", 1/2", 5/8" and 3/4" O.D. tubing.
- Cat. No. 89021 Flares 3/16", 1/4", 5/16", 3/8", 7/16", 1/2" and 5/8"
   O.D. tubing.

Cat. No.	Dimensions	Weight
89020	6-1/8" L (157 mm) x 6-1/2" W (165 mm) x 4-13/32" H (112 mm)	4.71 lbs.
89021	7" (178 mm) L x 4-13/16" W (122 mm) x 3-9/32" H (236 mm)	2.0 lbs.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

## **Duct Stretching & Slitting Tools**

#### **Duct Stretcher**



89565

- Aligns and pulls ductwork together, easing installation of drive cleats.
- Offset handle protects hand.

Cat. No.	Overall Length	Weight (oz.)
89565	16" (406 mm)	12

#### **Duct Slitting Tool**



- Blade used to scribe a line or pierce and enlarge holes in sheet metal.
- · Cushion-Grip handle for greater comfort and control.
- Patented Tip-Ident<sup>®</sup> quickly identifies the type of tool and tip orientation.

Cat. No.	Overall Length	Weight (oz.)
DS7	12-5/8" (321 mm)	5.6

## **Crimping Tools**

#### **5-Blade Crimper**

- Produces factory-precision indentations in stove pipe and round duct with just a squeeze.
- Compound-leverage mechanism, heavy-duty jaw/handle linkage, and closing stop provide easy operation and consistent crimps for virtually leak-proof connections.
- Hardened steel handles include hand guards covered with vinyl grips for added comfort and easy operation.
- All steel construction and nickel-plating provide long life and consistent crimp profile.

Cat. No.	Overall Length	Crimps	Handle Color	Weight (lbs.)
86550	9" (229 mm)	24 ga. CRSM and 28 ga. SSSM	blue	1.00



## **Sheet Metal Fasteners**

## **Self-Piercing Sheet Metal Screws**

- Zinc plated.
- Sheet metal screws with self piercing tips.
- Slotted 1/4" hex head washer.



8910-3/4

Cat. No.	Length	Driver Type	Size	Qty	Head Type
8910-3/4	3/4" (19 mm)	1/4" slotted	#8	1000	hex washer
8910-1/2	1/2" (13 mm)	1/4" slotted	#8	1000	hex washer

## **Magnetic Hex Drivers**

#### **Magnetic Hex Drivers**

- For driving sheet metal screws.
- Strong Rare Earth magnets for maximum holding.
- 1/4" hex shank with quick release groove.



86602

Cat. No.	Description	Overall Length	Weight (lbs.)
3-Pack			
86600	1/4" magnetic hex driver – 3 pack	1-3/4" (45 mm)	.12
86601	5/16" magnetic hex driver – 3 pack	1-3/4" (45 mm)	.14
86602	3/8" magnetic hex driver – 3 pack	1-3/4" (45 mm)	.16
10-Pack Punch Card for Individual Sale			
86600-10	1/4" magnetic hex driver	1-3/4" (45 mm)	.43
86601-10	5/16" magnetic hex driver	1-3/4" (45 mm)	.49
86602-10	3/8" magnetic hex driver	1-3/4" (45 mm)	.57

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



# HVAC



## **Refrigeration Wrenches**

#### **Ratcheting Refrigeration Wrenches**

- Fully reversible ratchet wrenches designed for refrigeration packing gland nuts and valve stem sockets.
- Also designed for beam-clamp installation.
- Wrenches are compact in size, with clearly marked sockets for four nut sizes.
- Quick-flip reversing lever permits instant ratchet reversal.
- Wrenches are ruggedly built and have polished chrome finish with smooth edges for comfort.



68310

Cat. No.	Socket Sizes	Length	Weight (lbs.)
68309	3/16" and 1/4" sq. x 1/2" and 9/16" hex	6-13/16" (173 mm)	.43
68310	3/16" and 5/16" sq. x 1/4" and 3/8" sq.	5-1/2" (140 mm)	.20
68310-24	24 pack of Cat. No. 68310	5-1/2" (140 mm)	4.70

## **Nylon Tie Tensioning Tools**

#### **Nylon Tie Tensioning Tools**

- Designed for work with ties rated at 120 - 250 lbs. (54 - 113 kg).
- Tensions up to 65 lbs. of force (30 kg).
- Maximum tie width of 15/32" (12 mm).
- Handle grips for comfort.
- Excess tie material is automatically cut off (Cat. No. 86571 only).

Cat. No.	Description	Weight (lbs.)
86570	nylon tie tensioning tool – manual	0.87
86571	nylon tie tensioning tool – automatic	1.01





## **Special-Purpose Knives**

#### **Serrated Duct Knife**

- Cuts duct board and flexible duct.
- Double-edged knife regular and serrated.
- Cushion-grip handle for comfort.
- Includes puncture resistant nylon sheath with belt loop.

Cat. No.	Blade Steel	Blade Length	Weight (lbs.)
DK06	stainless steel	5.5" (140 mm)	0.53



DK06



## **Specialty Screwdrivers**

## 11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/Installation Bit

#### Additional Features:

- Includes unique style bit for installation/removal of common TR-4 Schrader<sup>®</sup> valves and aggressive thread extractor tip for backing out broken cores.
- Great for HVAC and other industrial applications.
- Cushion-Grip handle for greater torque and comfort.
- Blast finish bit tips provide a firm hold and reduce cam out.





32527



Schrader® is a registered trademark of Schrader International, Inc.

Cat. No.	Contains	Weight (lbs.)
32527	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, #1 square and #2 square, 1/4" and 3/16" slotted, Schrader <sup>®</sup> valve core removal/installation – extractor	.44

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

## **Hammers**

#### **Setting Hammer**



- Durable epoxy resin handle helps to protect neck from fraying and splintering if incorrectly struck or over struck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Cushioned, PVC grip bonded to handle.
- Special high-carbon steel, octagon shaped head with flat striking surface and rounded cross peen.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
820-16	16 oz. (454 g)	13" (330 mm)	1.6

#### **Riveting Hammer**



- High-carbon steel round head is forged and hardened.
- Flat striking surface with rounded cross peen.
- Straight-grain American hickory handle is stained and lacquered.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
821-12	12 oz. (340 g)	12-1/4" (311 mm)	1.1

#### **Dead Blow Hammers**



- Durable, abrasion resistant non-marring hammer face.
- Increased striking force with zero impact rebound.
- Design isolates user from striking impact and reduces fatigue.
- 40% more driving power than other dead blow hammers.
- Protects job surface from damage.
- Applications: HVAC, metal fabrication, electronics, oil and mining, wood and metal assembly, automotive, aerospace.

Cat. No.	Overall Length	Head Weight	Weight (lbs.)
811-16	12.5" (318 mm)	16 oz. (454 g)	1.44
811-32	18" (457 mm)	32 oz. (908 g)	1.8



All dimensions are in inches and (millimeters).

## **Flexible Drill Bits**

#### **Flex Bit Augers**



Used to drill holes through wood within a wall.

- Tapered back for easy bit retrieval.
- Spring steel shaft resists deformation.
- Screw point tip pulls the bit through wood.
- Hole in tip allows for use with wire or cable pulling grip.

Cat. No.	Length	Weight (lbs.)
53716	3/8" x 54" (9.5 mm x 1372 mm)	1.00
53717	3/8" x 72" (9.5 mm x 1829 mm)	1.00
53718	9/16" x 54" (14 mm x 1372 mm)	1.00
53719	3/4" x 54" (19 mm x 1372 mm)	2.00
53751	3/4" x 72" (19 mm x 1829 mm)	2.00
53720	1" x 54" (25 mm x 1829 mm)	2.00







53719

53722



#### **Flex Bit Extensions**



• Connects to the end of a flex bit and extends the length.

Cat. No.	For Use with Flex Bits	Length	Connection Diameter	Weight (lbs.)
53722	3/4" and larger	54" (1372 mm)	5/8" (14 mm)	1.00
53723	9/16" and smaller	54" (1372 mm)	7/16" (11 mm)	1.00

#### **Flex Bit Placement Tool**

- For use with flexible drill bits.
- Positions flexible drill bits horizontally or vertically within a wall.
- Cushion Grip handle for non-slip comfort.
- Folding design stores more compactly than standard tool.



Cat. No.	Length	Weight (lbs.)
53715	11" (279 mm)	1.00

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits.

 $\textbf{NOTE:} \ \ \text{Read and follow safety instructions in power tool owner's manual.}$ 



## **Pulling Grips**

#### **Pulling Grips**





KPS075



- Used to pull wire or cable through walls.
- Pulling grip attaches to the hole in the tip of the flex bit; wire mesh holds the wire during the pull.
- Swivel end helps reduce twisting

Cat. No.	Capacity	Maximum Safe Load	Weight (lbs.)
KPS050	1/2" - 9/16" (12 mm - 14 mm)	100 lb	.07
KPS075	3/4" - 1" (19 mm - 25 mm)	185 lb	.11

**AWARNING:** Do not exceed maximum safe load as listed on the label attached to the product.

**AWARNING:** Always match proper size and type of grip to application.

**AWARNING:** Always inspect equipment before use.

## Flex Bit Kit

#### Flex Bit Kit


- 3-piece kit includes folding placement tool, 1/2"-9/16" O.D. pulling grip and 9/16" x 54" flexible drill bit.
- Everything you need to pull up to 9/16" O.D. wire.
- Complete kit used for drilling and pulling wire and cable.
- Use placement tool (Cat. No. 53715) to guide bit through walls.
- Flexible drill bit (Cat. No. 53718) makes 9/16" holes in wood.
- Pulling grip (Cat. No. KPS050) attaches to the flexible drill bit after the hole has been made and pulls 1/2" - 9/16" wire and cable.

Cat. No.	Kit Contains		Weight (lbs.)
53721			2.00
	Cat. No.	Description	
	53715	flex bit placement tool	
	53718	flex drill bit - 9/16" x 54" (14 mm x 1372 mm)	•
	KPS050	pulling grip - 1/2"-9/16" (12 mm - 14 mm)	•



All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.





## **Hole Saw Kits**

#### Master Electrician's Hole Saw Kit

- Includes the most commonly used saws and arbors.
- · All components are packed in a metal carrying case.

Cat. No.	Set Contai	ins			We
31640					8.1
	Hole Saw	s	Arbors		
	Cat. No.	Size	Cat. No.	Size	
	31514	7/8"	31650	1/4"	_
	31518	1-1/8"	31660	7/16"	_
	31522	1-3/8"	31670	7/16"	_
	31528	1-3/4"			_
	31532	2"	1		
	31540	2-1/2"	1		
	31548	3"	1		
	31558	3-5/8"	1		
	31566	4-1/8"	1		
	31572	4-1/2"	1		
			_		

Note: Set pilot drill point 1/8" beyond tooth points.

#### **Large Size Hole Saw Kit**

- Contains the sizes necessary to upgrade an Electrician's Hole Saw Kit into a Master Electrician's set.
- All components are packed in a metal carrying case.

Cat. No.	Set Contai	ns			Weight (lbs.)
31645					6.60
	Hole Saws	s	Arbors		_
	Cat. No.	Size	Cat. No.	Size	
	31548	3"	31670	7/16"	
	31558	3-5/8"			_
	31566	4-1/8"	1		
	31572	4-1/2"			

Note: Set pilot drill point 1/8" beyond tooth points.

#### **Electrician's Hole Saw Kit**

- Contains the most popular sizes for basic electrical work.
- All components are packed in a rust-proof, molded plastic carrying case.

Gal. No.	Set Conta	IIIS			wei
31630					2.60
	Hole Saw	s	Arbors		
	Cat. No.	Size	Cat. No.	Size	
	31514	7/8"	31660	7/16"	_
	31518	1-1/8"	31670	7/16"	
	31522	1-3/8"			_
	31528	1-3/4"			
	31532	2"	1		
	31540	2-1/2"	1		

ight (lbs.)

Note: Set pilot drill point 1/8" beyond tooth points.

All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

**AWARNING:** Never use on or near live electrical circuits.



- The most frequently used sizes and an arbor extension for hard to reach spots.
- All components are packed in a rust-proof, molded plastic carrying case.

**Set Contains** 

31635					4.50
	Hole Saws	S	Arbors		
	Cat. No.	Size	Cat. No.	Size	
	31512	3/4"	31650	1/4"	_
	31514	7/8"	31660	7/16"	_
	31518	1-1/8"	31670	7/16"	_
	31522	1-3/8"			_
	31524	1-1/2"	Arbor Exte	ender	
	31528	1-3/4"	Cat. No.	Size	
	31532	2"	31678	12"	_
	31536	2-1/4"			_
	31540	2-1/2"	1		

Note: Set pilot drill point 1/8" beyond tooth points.





Weight (lbs.)

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.

# LE IA

## **Hole Saws**

#### **Bi-Metal Hole Saws**

- Cuts through steel, wood, plastic, stainless steel, and cast iron.
- Rugged bi-metal cobalt construction for heavy-duty cutting.
- Deep cup cuts through studs in one pass.
- Variable pitch teeth for faster, smoother cutting and less vibration.
- Longer lasting design for more cuts per saw.
- Multiple knock-out slots and holes for easy core removal.





31532

Cat. No.	Saw Diameter	Pipe Tap Size*	Pipe Entr. Size**	For Use with Arbor No.	Weight (lbs.)
31510	5/8" (16 mm)	_	_	31650, 31655, 31660	.05
31512	3/4" (19 mm)	1/2" (13 mm)	3/8" (10 mm)	31650, 31655, 31660	.06
31514	7/8" (22 mm)	3/4" (19 mm)	1/2" (13 mm)	31650, 31655, 31660	.60
31516	1" (25 mm)	_	_	31650, 31655, 31660	.07
31518	1-1/8" (29 mm)	1" (25 mm)	3/4" (19 mm)	31650, 31655, 31660	.08
31520	1-1/4" (32 mm)	_	_	31665, 31670	.09
31522	1-3/8" (35 mm)	_	1" (25 mm)	31665, 31670	.12
31524	1-1/2" (38 mm)	1-1/4" (32 mm)	_	31665, 31670	.09
31526	1-5/8" (41 mm)	_	_	31665, 31670	.10
31528	1-3/4" (44 mm)	1-1/2" (38 mm)	1-1/4" (32 mm)	31665, 31670	.11
31532	2" (51 mm)	_	1-1/2" (38 mm)	31665, 31670	.13
31534	2-1/8" (54 mm)	_	_	31665, 31670	.14
31536	2-1/4" (57 mm)	2" (51 mm)	_	31665, 31670	.15
31538	2-3/8" (60 mm)	_	_	31665, 31670	.16
31540	2-1/2" (64 mm)	_	2" (51 mm)	31665, 31670	.17
31542	2-5/8" (67 mm)	2-1/2" (64 mm)	_	31665, 31670	.18
31544	2-3/4" (70 mm)	_	_	31665, 31670	.19
31548	3" (76 mm)	_	2-1/2" (64 mm)	31665, 31670	.22
31552	3-1/4" (83 mm)	3" (76 mm)	_	31665, 31670	.26
31556	3-1/2" (89 mm)	_	_	31665, 31670	.28
31558	3-5/8" (92 mm)	_	3" (76 mm)	31665, 31670	.29
31564	4" (102 mm)	_	_	31665, 31670	.33
31566	4-1/8" (105 mm)	_	3-1/2" (89 mm)	31665, 31670	.36
31568	4-1/4" (108 mm)	4" (102 mm)	_	31665, 31670	.36
31572	4-1/2" (114 mm)	_	4" (102 mm)	31665, 31670	.40
31576	4-3/4" (121 mm)	_	_	31665, 31670	.50
31580	5" (127 mm)	_	_	31665, 31670	.54
31596	6" (152 mm)	_	_	31665, 31670	.75
31600SEN	6-3/8" (162 mm)	_	_	31665, 31670	2.00
31606	6-5/8" (168 mm)	_	_	31665, 31670	2.25

Note: Set pilot drill point 1/8" beyond tooth points.

Note: Pipe sizes listed in the "Pipe Tap Size" and "Pipe Entrance Size" columns are standard industry sizes. All pipes are sized by the nominal inside diameter.

All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.

<sup>\*</sup>Pipe Tap Size — The sizes listed provide the necessary information whenever a pipe is to be threaded into tanks, boilers, etc. To secure the best results, the hole should be reamed before tapping with a reamer having a taper of 3/4" per foot.

<sup>\*\*</sup>Pipe Entrance Size – The sizes listed provide the necessary information for any given pipe size to have sufficient clearance to pass through beams, walls, bulkheads, etc.

## **Hole Saws**

#### **Carbide Grit Hole Saws**

- Available in the most common sizes for recessed can lights.
- · Carbide grit for smooth cuts and minimal tear out.
- Long-lasting carbide grit will not dull in abrasive materials.
- Grit design reduces the kick when starting a cut in plywood.
- Cuts through drywall, ceiling tile, lathe/plaster, cement board and wood.

Cat. No.	Saw Diameter	For Use with Arbor No.	Weight (lbs.)
31605	6-3/8" (161 mm)	31168, 31665, 31670	1.65
31607	6-5/8" (168 mm)	31168, 31665, 31670	1.65
31611	6-7/8" (174 mm)	31168, 31665, 31670	1.75

Note: Set pilot drill point 1/8" beyond tooth points.



#### **Hole-Saw Arbors and Accessories**

- 118º split point pilot bits.
- Hardened mandrels for long thread life.







Note: Set pilot drill point 1/8" beyond tooth points.





31678

Cat. No.	Shank Style	Pins	Shank Size	Electric Drill Size	Thread Size	Weight (lbs.)
31650	round tri-lobe	N	1/4" (6 mm)	1/4" and larger	1/2" - 20	.14
31655	hexagonal	N	3/8" (10 mm)	3/8" and larger	1/2" - 20	.16
31660	hexagonal	N	7/16" (11 mm)	1/2" and larger	1/2" - 20	.16
31665	hexagonal	N	7/16" (11 mm)	1/2" and larger	5/8" - 18	.50
31670	hexagonal	Threaded	7/16" (11 mm)	1/2" and larger	5/8" - 18	.55
Replacement	Pilot Drills for Hole-Sa	w Arbors				
31672	1/4" Replacement Pile	ot Drill Bit for Klein Arbo	ors 31650, 31660, 31665, 31	670		.02
31674	1/4" Replacement Pile		.04			
31676	Arbor Adapter; conve	.03				
31678	12" Arbor Extender*		7/16" (11 mm)	1/2" and larger	-	.77

## **Adjustable Hole Saw**

- Quickly and smoothly cuts cleaner holes in drywall and ceiling tiles.
- Blades adjust to cut holes from 2" to 7" in diameter.
- Fits most 3/8" and 1/2" drill chucks.
- No binding while cutting.
- No additional tools needed to adjust the hole saw.
- Newly redesigned dust shield (two included) for longer life.
- Hex key included.

Cat. No.	Range	Weight (lbs.)
53731	2" - 7" (51 mm - 177 mm)	.31

All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

**AWARNING:** Never use on or near live electrical circuits.



**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.





## **Carbide-Tipped Hole Cutters**

#### **Carbide Hole Cutter**

Cat. No.	Size	Conduit & Pipe Size	es Weight (lbs.)		
31850	3/4"	-	.25		
31852	7/8"	1/2"	.30		
31854	1"	-	.35		
31856	1-1/8"	3/4"	.40		
31857	1-7/32"	-	.40		
31858	1-1/4"	-	.40		
31860	1-3/8"	1"	.45		
31862	1-7/16"	_	.40		
31864	1-1/2"	-	.45		
31866	1-3/4"	1-1/4"	.70		
31868	2"	1-1/2"	.80		
31870	2-1/2"	2"	.95		
Replacement Parts					
31874	replacement	hole cutter pilot bit	.05		



- Cuts quick, precise holes in stainless steel, mild steel, iron, copper and brass sheet up to 3/16" (5 mm) thick.
- Smooth start pilot drill bit for greater control.
- Split point pilot drill bit prevents bit walking.
- Integrated flange prevents the operator from drilling beyond the sheet metal.
- Ejection spring for easy slug removal.

## **Carbide-Tipped Hole Cutter Kits**

#### **4-Piece Carbide Hole Cutter Kit**

- Cuts quick, precise holes in stainless steel, mild steel, iron, copper and brass sheet up to 3/16" (5 mm) thick.
- Split point pilot drill bit prevents bit walking.
- Integrated flange prevents the operator from drilling beyond the sheet metal.
- Conduit and pipe sizes: 1/2"- 1".

Cat. No.	Set Contains		Weight (lbs.)
31872	Carbide Hole Cutters		1.45
	Cat. No.	Size	
	31852	7/8"	
	31856	1-1/8"	
	31860	1-3/8"	
	extra pilot bit		

## 8-Piece Master Electrician's Hole Cutter Kit

- Cuts quick, precise holes in stainless steel, mild steel, iron, copperand brass sheet up to 3/16" (5 mm) thick.
- Split point pilot drill bit prevents bit walking.
- Integrated flange prevents the operator from drilling beyond the sheet metal.
- Conduit and pipe sizes: 1/2"-2"

Cat. No.	Set Contains		Weight (lbs.)
31873	Carbide Hole	Cutters	4.30
	Cat. No.	Size	
	31852	7/8"	
	31856	1-1/8"	<del></del>
	31860	1-3/8"	
	31866	1-3/4"	
	31868	2"	
	31870	2-1/2"	
	2 extra pilot bits		





All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

AWARNING: Never use on or near live electrical circuits

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.

## **Knockout Punches**

#### **Knockout Punch Set**

- Optimized design reduces wrench effort.
- Slugs are split inside for easy removal.
- Maximum capacity of 10 gauge mild steel.
   Also cuts aluminum, fiberglass and plastic.
- Punches holes cleanly and accurately.
- Set includes 1/2" or 3/4" punch and die with draw stud.

Cat. No.	Overall Length	Conduit Size	Weight (lbs.)
53727	4" (102 mm)	3/4" (19 mm)	.98
53728	2-5/8" (67 mm)	1/2" (12.5 mm)	.45



#### **Knockout Punch Set with Wrench**

- Set includes: 1" ratcheting wrench, knockout punches, dies and draw studs for 1/2", 3/4", 1", 1-1/4", 1-1/2", and 2" conduit sizes.
- Cutting capacity 10 gauge mild steel; also cuts aluminum, fiberglass and plastic.
- Splits slugs for easy removal.
- Punches holes cleanly and accurately.
- Kit includes six different size knockout punches and dies, two draw studs and one ratcheting box end wrench.



53732

Cat. No.					Weight (lbs.)
53732					9.00
	Punch Cat. No.	Die Cat. No.	Description	Conduit Size	
	53819	53820	knockout punch	1/2" (13 mm)	
	53827	53828	knockout punch	3/4" (19 mm)	
	53837	53838	knockout punch	1" (25 mm)	
•	53849	53850	knockout punch	1-1/4" (32 mm)	
	53857	53858	knockout punch	1-1/2" (38 mm)	
	53867	53868	knockout punch	2" (51 mm)	
	Cat. No.		Description	Size	
·	53873		ratcheting wrench	1" (25 mm)	
•	53871		draw stud	3/8" x 2-5/8" (9.5 mm x 67 mm)	
	53872		draw stud	3/4" x 4" (19 mm x 102 mm)	

**AWARNING:** Do NOT push or hammer wrench.

**AWARNING:** Do NOT extend handle length of wrench.



All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

AWARNING: Never use on or near live electrical circuits.

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.





## **Step-Drill Bits**

#### High Speed Steel Step-Drill Bits — Inch

- Single-fluted design eliminates skidding and makes for easier resharpening.
- Laser-etched hole sizes are easy-to-read and permanent.
- Anti-skid tip eliminates the need for center punching or pilot hole drilling for most sizes.
- Drill multiple-size holes in thin sections of metal, plastic and wood using a single bit.
- Works in most metals (steel, brass, aluminum, copper), as well as in plastic and wood.



Cat. No.	Quick Reference Number	No. of Hole Sizes per Bit	Size Range (Hole Diameter)	Pilot Hole Required	Electric Drill Size	Depth Penetration for Each Step	Weight (lbs.)
59001	1	13 in 1/32" increments	1/8" to 1/2"	no	1/4" and larger	1/8"	.05
59002	2	8 in 1/16" increments	9/16" to 1"	yes, 1/2" or larger	1/2" and larger	1/8"	.20
59003	3	9 in 1/16" increments	1/4" to 3/4"	no	3/8" and larger	1/8"	.15
59004	4	10 in 1/8" increments	13/16" to 1-3/8"	yes, 3/4" or larger	1/2" and larger	1/8"	.50
59005	5	6 in 1/16" increments	3/16" to 1/2"	no	1/4" and larger	3/8"	.05
59008	8	1	7/8"	no	3/8" and larger	not applicable	.10
59009	9	10 in 1/8" increments	1/4" to 1-3/8"	no	1/2" and larger	1/8"	.46
59011	11	2	7/8" and 1-1/8"	no	1/2" and larger	1/8"	.30
59014	14	12 in 1/16" increments	3/16" to 7/8"	no	3/8" and larger	1/8"	.15



- Similar to Klein high-speed steel step-drill bits, but with a titanium-nitride coating (82 – 86 Rockwell C hardness).
- Coating reduces friction for cooler, smoother running without lubrication; allows bits to last up to 4 to 5 times longer than steel drill bits.
- Single-fluted design eliminates skidding and makes for easier resharpening.
- Laser-etched hole sizes are easy-to-read and permanent.
- Bits are perfect for drilling accurate, round holes in thin (up to 1/8') metal (steel, brass, aluminum and copper), as well as plastic and wood.
- Anti-skid tip eliminates the need for center punching or pilot hole drilling.



Cat. No.	Quick Reference Number	No. of Hole Sizes per Bit	Size Range (Hole Diameter)	Pilot Hole Required	Electric Drill Size	Depth Penetration for Each Step	Weight (lbs.)
59001T	1T	13 in 1/32" increments	1/8" to 1/2"	no	1/4" and larger	1/8"	.10
59003T	3T	9 in 1/16" increments	1/4" to 3/4"	no	3/8" and larger	1/8"	.15
59005T	5T	6 in 1/16" increments	3/16" to 1/2"	no	1/4" and larger	3/8"	.05
59009T	9	10 in 1/8" increments	1/4" to 1-3/8"	no	1/2" and larger	1/8"	.46
5001/IT	1/IT	12 in 1/16" increments	3/16" to 7/8"	nn	3/8" and larger	1/8"	15

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Never use on or near live electrical circuits

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.

286

NOTE: Read and follow safety instructions in power tool owner's manual.

## **Step-Drill Bits**

#### **Cobalt Step-Drill Bits**

- Similar to Klein high-speed steel step-drill bits, but with a cobalt finish.
- Coating reduces friction for cooler, smoother running without lubrication; allows bits to last longer than ordinary bits.
- Single-fluted design eliminates skidding and makes for easier resharpening.
- Laser-etched hole sizes are easy-to-read and permanent.
- Bits are perfect for drilling accurate, round holes in thin (up to 1/8") metal (steel, brass, aluminum and copper), as well as plastic and wood.
- Anti-skid tip eliminates the need for center punching or pilot hole drilling.



0001	59034
59031	59U34

Cat. No.	No. of Hole Sizes per Bit	Size Range (Hole Diameter)	Pilot Hole Required	Electric Drill Size	Depth Penetration for Each Step	Weight (lbs.)
59031	9 in 1 mm increments	4 mm to12 mm	no	1/4" and larger	5 mm	.05
59034	10 in 2 mm increments	4 mm to 22 mm	no	3/8" and larger	3.5 mm	.14

## **Ship-Auger Bits**

#### **Ship-Auger Bits with Screw Point**

- Bits drill through nails, wood, vinyl, plastics and heavy timber.
- Special bit steel with machine-ground flutes and polished edges for smooth, wobble-free boring.
- Feed-screw pilot draws bit into wood.
- Full length is heat-treated and tempered.
- Deep, open-throat design clears chips for faster, cleaner cuts.
- Shanks are 7/16" hex to fit 1/2" and larger three-jaw chucks.

Cat. No.	Bit Size	Twist Length	Overall Length	Weight (lbs.)
53401	11/16"	4" (102 mm)	6" (152 mm)	.30
53402	3/4"	4" (102 mm)	6" (152 mm)	.40
53403	13/16"	4" (102 mm)	6" (152 mm)	.40
53404	7/8"	4" (102 mm)	6" (152 mm)	.50
53405	15/16"	4" (102 mm)	6" (152 mm)	.50
53406	1"	4" (102 mm)	6" (152 mm)	.50
53407	1-1/16"	4" (102 mm)	6" (152 mm)	.60
53408	1-1/8"	4" (102 mm)	6" (152 mm)	.80
53409	1-1/4"	4" (102 mm)	6" (152 mm)	1.00
53410	1-3/8"	4" (102 mm)	6" (152 mm)	.80
53411	1-1/2"	4" (102 mm)	6" (152 mm)	.90
53430	1-1/8"	4-3/4" (121 mm)	7-3/4" (197 mm)	.80
53434	9/16"	15" (381 mm)	18" (457 mm)	.65



53430

- Head and twist are ground to correct clearance for easy removal from hole.
- For heavy construction and repair work in mines, on docks and bridges, and for electrical work.

Cat. No.	Bit Size	Twist Length	Overall Length	Weight (lbs.)
53435	5/8"	15" (381 mm)	18" (457 mm)	.80
53436	11/16"	15" (381 mm)	18" (457 mm)	.85
53437	3/4"	15" (381 mm)	18" (457 mm)	.95
53438	13/16"	15" (381 mm)	18" (457 mm)	1.05
53439	7/8"	15" (381 mm)	18" (457 mm)	1.20
53440	15/16"	15" (381 mm)	18" (457 mm)	1.50
53441	1"	15" (381 mm)	18" (457 mm)	1.70
53442	1-1/16"	15" (381 mm)	18" (457 mm)	1.95
53443	1-1/8"	15" (381 mm)	18" (457 mm)	1.80
53444	1-1/4"	15" (381 mm)	18" (457 mm)	2.20
53445	1-3/8"	15" (381 mm)	18" (457 mm)	2.80
53446	1-1/2"	15" (381 mm)	18" (457 mm)	3.45

All dimensions are in inches and (millimeters) unless otherwise specified.

AWARNING: Never use on or near live electrical circuits.

**NOTE:** Read and follow safety instructions in power tool owner's manual.

 $\hat{\textbf{AWARNING:}}$  Always ensure that you and persons in the vicinity wear approved eye protection.





# **Drill Bit Sets**

#### 13-Piece Regular-Point Drill-Bit Set

• Hinged metal box with one stand-up bit holder.

Cat. No.	Set Contair	IS .			Weight (lbs.)
53002					.60
	Cat. No.	Bit Size	Cat. No.	Bit Size	
	53100	1/16"	53107	11/64"	_
	53101	5/64"	53108	3/16"	_
	53102	3/32"	53109	13/64"	_
	53103	7/64"	53110	7/32"	_
	53104	1/8"	53111	15/64"	_
	53105	9/64"	53112	1/4"	_
	53106	5/32"			



#### 15-Piece Regular-Point Drill-Bit Set

• Hinged metal box with two stand-up bit holders.

-			•		
Cat. No.	Set Contair	IS .			Weight (
53001					2.00
	Cat. No.	Bit Size	Cat. No.	Bit Size	
	53100	1/16"	53116	5/16"	
	53102	3/32"	53118	11/32"	_
	53104	1/8"	53120	3/8"	_
	53106	5/32"	53122	13/32"	_
	53108	3/16"	53124	7/16"	_
	53110	7/32"	53126	15/32"	_
	53112	1/4"	53128	1/2"	_
	53114	9/32"			_
			_		



#### 29-Piece Regular-Point Drill-Bit Set

Hinged metal box with three stand-up bit holders.

Cat. No.	Set Contains			Weight (lbs.)	
53000					3.25
	Cat. No.	Bit Size	Cat. No.	Bit Size	
	53100	1/16"	53115	19/64"	
	53101	5/64"	53116	5/16"	•
	53102	3/32"	53117	21/64"	
	53103	7/64"	53118	11/32"	-
	53104	1/8"	53119	23/64"	
	53105	9/64"	53120	3/8"	•
	53106	5/32"	53121	25/64"	
	53107	11/64"	53122	13/32"	-
	53108	3/16"	53123	27/64"	
	53109	13/64"	53124	7/16"	•
	53110	7/32"	53125	29/64"	_
	53111	15/64"	53126	15/32"	-
	53112	1/4"	53127	31/64"	-
	53113	17/64"	53128	1/2"	-
	53114	9/32"			<u>-</u>



All dimensions are in inches and (millimeters) unless otherwise specified.

NOTE: Read and follow safety instructions in power tool owner's manual.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always ensure that you and persons in the vicinity wear approved eye protection.

#### **Drill Bits**

#### Regular-Point 118° High-Speed Drill Bits

- General-purpose, high-speed bits for reliable performance in a wide range of materials.
- Standard jobber length.
- Black-oxide finish reduces chip welding.
- Lightly roughened surface has higher lubricity for easier chip flow.

Cat. No.	Bit Size	Flute Length	Overall Length	Weight (lbs.)
53100	1/16"	7/8" (22 mm)	1-7/8" (48 mm)	.01
53101	5/64"	1" (25 mm)	2" (51 mm)	.01
53102	3/32"	1-1/4" (32 mm)	2-1/4" (57 mm)	.01
53103	7/64"	1-1/2" (38 mm)	2-5/8" (67 mm)	.01
53104	1/8"	1-5/8" (41 mm)	2-3/4" (70 mm)	.01
53105	9/64"	1-3/4" (44 mm)	2-7/8" (73 mm)	.01
53106	5/32"	2" (51 mm)	3-1/8" (79 mm)	.01
53107	11/64"	2-1/8" (54 mm)	3-1/4" (83 mm)	.01
53108	3/16"	2-5/16" (59 mm)	3-1/2" (89 mm)	.02
53109	13/64"	2-7/16" (62 mm)	3-5/8" (92 mm)	.02
53110	7/32"	2-1/2" (64 mm)	3-3/4" (95 mm)	.05
53111	15/64"	2-5/8" (67 mm)	3-7/8" (98 mm)	.05
53112	1/4"	2-3/4" (70 mm)	4" (102 mm)	.05
53113	17/64"	2-7/8" (73 mm)	4-1/8" (105 mm)	.05
53114	9/32"	2-15/16" (75 mm)	4-1/4" (108 mm)	.05



53115	19/64"	3-1/16" (78 mm)	4-3/8" (111 mm)	.05
53116	5/16"	3-3/16" (81 mm)	4-1/2" (114 mm)	.05
53117	21/64"	3-5/16" (84 mm)	4-5/8" (117 mm)	.10
53118	11/32"	3-7/16" (87 mm)	4-3/4" (121 mm)	.05
53119	23/64"	3-1/2" (89 mm)	4-7/8" (124 mm)	.10
53120	3/8"	3-5/8" (92 mm)	5" (127 mm)	.10
53121	25/64"	3-3/4" (95 mm)	5-1/8" (130 mm)	.10
53122	13/32"	3-7/8" (98 mm)	5-1/4" (133 mm)	.15
53123	27/64"	3-15/16" (100 mm)	5-3/8" (137 mm)	.15
53124	7/16"	4-1/16" (103 mm)	5-1/2" (140 mm)	.15
53125	29/64"	4-3/16" (106 mm)	5-5/8" (143 mm)	.18
53126	15/32"	4-5/16" (110 mm)	5-3/4" (146 mm)	.15
53127	31/64"	4-3/8" (111 mm)	5-7/8" (149 mm)	.20
53128	1/2"	4-1/2" (114 mm)	6" (152 mm)	.20

#### 4-Piece, Carbide-Tipped, Masonry **Drill Bit Set**



53004

Protective plastic storage pouch.

Cat. No.	Set Contains		Weight (lbs.
53004			.30
	Cat. No.	Bit Size	
	53175	1/4"	
	53176	5/16"	
	53177	3/8"	
	53178	1/2"	

#### **Carbide-Tipped, Masonry Drill Bits**



53178

53729

- Drills through hard materials such as brick, concrete, plaster, and tile.
- Black-oxide finish reduces chip welding.

Cat. No.	Bit Size	Shank Diameter	Overall Length	Weight (lbs.)
53175	1/4"	1/4"	4" (102 mm)	.05
53176	5/16"	1/4"	4" (102 mm)	.05
53177	3/8"	1/4"	4" (102 mm)	.05
53178	1/2"	1/4"	4" (102 mm)	.10

### **Anchors**


#### Conical Anchor Kit – 100 Fasteners

- Kit contains: 100 #2 Phillips, 10 x 1" Screws, and 100 plastic anchors.
- 1/4" Masonry drill bit also included.


Cat. No.	Anchor Size	Screw Size	Bit Size	Weight (lbs.)
53729	10 - 12	10 x 1" (25 mm)	1/4" (6 mm)	1.00

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\textbf{NOTE:} \ \ \text{Read and follow safety instructions in power tool owner's manual}.$ 











#### Saws & Blades

#### **High-Tension Hack Saw**

- Adjustable blade tension up to 30,000 PSI for fast, precise cuts.
- Soft-touch grips.
- Alternative 45 degree mounting for flush cutting.
- Front mount for reciprocating saw blades.
- Blade storage in handle.
- Includes 12" x 24 TPI bi-metal hack saw blade and 6" x 24 TPI bi-metal reciprocating saw blade.



702-12

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
702-12	12" (305 mm)	16-1/4" (413 mm)	1.45

#### **Heavy-Weight Hacksaws**

- A rugged, heavy-duty saw with the versatility to satisfy professional requirements.
- Greater weight means a faster job.
- · Permits efficient one-hand use where necessary.
- Blade cuts fully through to a flat surface.
- Converts easily from vertical to horizontal position for full-flush cutting.
- Durable, tubular steel frame and die-cast zinc handles with blue finish.
- Pivot-action front end with slotted tensioning rod permits maximum tightening of blade for more efficient sawing and longer blade life.
- Curved front-end design for comfortable two-hand use.
- Storage for extra blades in tubular steel frame.



701-10

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
701-10	10" (254 mm)	14" (356 mm)	2.05
701-12	12" (305 mm)	16" (406 mm)	2.10

#### Dual-Purpose Hacksaw — Golden Tri-Cut™ 3-in-1 Blade

- Blade has three teeth sizes.
- Blade converts quickly to 90° or 45° for standard or flush-cut applications.
- Pivot-lock adjusts blade tension for straighter cuts and longer blade life.
- Set screw allows for storage of extra blades and secures blade for "jab" sawing.
- Aluminum finger grip handle and front end.
- Thumb guard for two-hand sawing.



Cat. No.	Blade Length	Overall Length	Weight (lbs.)
701-S	12" (305 mm)	16" (406 mm)	1.45



701-S



All dimensions are in inches and (millimeters)

**AWARNING:** Always wear approved eye protection.

#### Saws & Blades

#### **Bi-Metal Blades**

1224BI

- Special high-speed steel teeth fused to regular carbon-steel body, which provides superior cutting and longer life.
- Withstands greater saw tension for less blade flexing.
- Fits all 12" (305 mm) hacksaw blades.
- Blue finish.
- Available in box of 100 blades or in a reclosable, heavy-vinyl, seal-tight pouch of ten blades.

Cat. No.	Pack Size	Teeth Per Inch	Length	Weight Per Pack (lbs.)
1218BI-P	10-pack	18	12" (305 mm)	.45
1224BI-P	10-pack	24	12" (305 mm)	.45
1232BI-P	10-pack	32	12" (305 mm)	.45
1218BI	100-pack	18	12" (305 mm)	4.50
1224BI	100-pack	24	12" (305 mm)	4.50
1232BI	100-pack	32	12" (305 mm)	4.50

#### Golden Tri-Cut™ Blades

COLUMN CATES TO BE WAS TO BE WANTED TOOLS OF THE PARTY OF

Blade has three teeth sizes

- Unique design provides three teeth sizes on one blade.
- Has 32 teeth/inch up front for quick starts, 24 teeth/inch in the middle and 18 teeth/inch on the end for fast and smooth conventional cutting.
- Special high-speed steel teeth fused to carbon-steel provide superior cutting action and long life.
- Gold finish.
- Available in box of 100 blades or reclosable, heavy-vinyl, seal-tight pouch of ten blades.

Cat. No.	Pack Size	Teeth Per Inch	Length	Weight Per Pack (lbs.)
1200BI-P	10-pack	32-24-18	12" (305 mm)	.45
1200BI	100-pack	32-24-18	12" (305 mm)	4.50

#### **Jab Saw**

- Cuts drywall, wallboard, plywood and plastic.
- Triple ground teeth for a fast cut.
- Blade cuts in both directions (push and pull).
- Hardened, carbon-steel blade for durability.
- Hardened, beveled blade point for scoring and plunge cuts.
- Comfort cushion grip with thumb groove.
- Handle structure designed for strength and durability.
- Flat-end grip for palming or punching through drywall.



725

1200BI

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
725	6" (152 mm)	12" (305 mm)	.31

**AWARNING:** Never use blade as a prying device as blades may break & cause injury.

#### **Magic-Slot Compass Saws**


- Magic-Slot design allows fast blade changing without removing thumbscrew.
- Handle is strong, lightweight, die-cast zinc with blue finish.
- · Handle is contoured for comfort.
- Blade is tough, high-quality carbon steel, 8" (203 mm) long, with ten teeth per inch for general-purpose use.
- Replacement blades and handle can be ordered separately.

Cat. No.	Description	Overall Length	Teeth Per Inch	Weight (lbs.)
703	Magic-Slot compass saw complete with Cat. No. 706 blade	13" (330 mm)	10	1.20
702	Magic-Slot compass saw handle only. Takes only Magic-Slot cut-in or general-purpose blades.	5" (127 mm)	_	1.10



703

#### **Compass Saw Blades**



 For cutting through wallboard or Masonite to install wiring, outlet boxes, etc.

- Tough high-quality carbon steel.
- Pointed starter tip.
- Fits Magic-Slot compass saw handle Cat. No. 702.

Blade Length	Teeth Per Inch	Weight (lbs.)
lectrician's Cut-in Bla	de	
4" (102 mm)	10	.06
ose Compass Saw Blad	des	
12" (305 mm)	8	.14
12" (305 mm)	10	.14
8" (203 mm)	10	.09
10" (254 mm)	10	.12
	### (102 mm) ### (305 mm) ### (203 mm) ### (203 mm) ### (203 mm)	(10ctrician's Cut-in Blade

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

# **Reciprocating Saw Blades**

#### **Premium Reciprocating Saw Blades**

- Heavy duty, bi-metal blades are 1" wide and .042 thick, which offers greater rigidity for smooth, straight, accurate cuts.
- Innovative tooth geometry and blade design for faster cutting, less vibration and longer blade life.
- Available in blade lengths of 6", 9" and 12" to meet a variety of cutting applications.
- 1/2" universal shank to fit all popular reciprocating saw tools.




31810

Cat. No.	Blade Length	TPI	Blade Width	Blade Thick- ness	Pack	Main Applications
31810	6"	10	1"	0.042	5	HD - Metal
31802	6"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31804	6"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"
31806	6"	24	1"	0.042	5	HD - Metals 18 ga. & under
31808	9"	10	1"	0.042	5	HD - Metal
31832	9"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31834	9"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"
31836	12"	10	1"	0.042	5	HD - Metal
31838	12"	14	1"	0.042	5	HD - Metals 1/8" thick & above
31840	12"	18	1"	0.042	5	HD - Metals 18 ga. to 1/8"

#### **Reciprocating Saw Blades**






 1/2" universal shank to fit all popular reciprocating saw tools.



31750



31722



Cat. No.	Blade Length	TPI	Blade Width	Blade Thickness	Pack	Main Applications
31738	8"	10/14	3/4"	0.035	5	Wood with nails
31738-15	8"	10/14	3/4"	0.035	15	Wood with nails
31742	8"	14	3/4"	0.035	5	Heavy ga. metals
31742-15	8"	14	3/4"	0.035	15	Heavy ga. metals
31746	8"	18	3/4"	0.035	5	Heavy ga. metals
31746-15	8"	18	3/4"	0.035	15	Heavy ga. metals
31750	9"	6	3/4"	0.050	5	Wood with nails
31750-15	9"	6	3/4"	0.050	15	Wood with nails
31754	9"	6	7/8"	0.062	3	Demo
31756	9"	10	7/8"	0.062	3	Demo
31758	12"	6	3/4"	0.050	5	Wood with nails
31758-15	12"	6	3/4"	0.050	15	Wood with nails
31762	12"	6	7/8"	0.062	3	Demo
31764	12"	10	7/8"	0.062	3	Demo
31766	12"	10/14	3/4"	0.050	5	Wood with nails



All dimensions are in inches and (millimeters)

**AWARNING:** Always wear approved eye protection.



# Knives & Cutting Tools

Klein provides a wide range of knives, scissors and other cutting tools for professional applications across all trades.




# **Pocket Knives - One Blade**

#### **Lightweight Lockback Knives**

- Blades are AUS 8 stainless steel hardened to 58-59 Rc.
- Premium quality blade offers superior edge holding.
- Impact-resistant nylon resin handle with rubber insert (Cat. Nos. 44002-44005).
- Slim and comfortable silver anodized-aluminum handle for corrosion-resistance (Cat. Nos. 44000, 44001, 44006, 44007).
- Black chrome blade and black anodized-aluminum handle for corrosion-resistance (Cat. Nos. 44000-BLK and 44001-BLK).
- · Reversible thumb stud provides easy one-handed opening.

Blade Steel	Blade Length	Length Closed	Weight (oz.)					
Drop Point Blade								
AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.5					
AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.1					
AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	2.5					
AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	1.3					
AUS 8 stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	1.5					
AUS 8 stainless steel	2-3/4" (70 mm)	4-1/8" (105 mm)	2.5					
Blade								
AUS 8 stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	1.5					
AUS 8 stainless steel	2-5/8" (67 mm)	4-1/8" (105 mm)	2.5					
AUS 8 stainless steel	2-5/8" (67 mm)	3-1/2" (89 mm)	1.3					
de								
AUS 8 stainless steel	2-1/2" (63 mm)	3-1/2" (89 mm)	1.5					
	AUS 8 stainless steel	### AUS 8 stainless steel	AUS 8 stainless steel 2-1/4" (57 mm) 3-1/8" (76 mm)  AUS 8 stainless steel 2-1/4" (57 mm) 3-1/8" (76 mm)  AUS 8 stainless steel 2-1/2" (64 mm) 3-1/2" (89 mm)  AUS 8 stainless steel 2-1/2" (64 mm) 3-1/2" (89 mm)  AUS 8 stainless steel 2-3/8" (60 mm) 3-1/2" (89 mm)  AUS 8 stainless steel 2-3/4" (70 mm) 4-1/8" (105 mm)  Blade  AUS 8 stainless steel 2-3/8" (60 mm) 3-1/2" (89 mm)  AUS 8 stainless steel 2-5/8" (67 mm) 4-1/8" (105 mm)  AUS 8 stainless steel 2-5/8" (67 mm) 3-1/2" (89 mm)					





44001-BLK



44001



44002



#### 44005

#### Money-Clip Pocket Knife — Spearpoint Blade and Nail File

- Handsome, brushed stainless steel case with rosewood insert.
- Includes money clip, 1-1/2" (38 mm) spearpoint blade and 1-1/2" (38 mm) nail file.

Cat. No.	Blade Type	Blade Length	Length Closed	Weight (oz.)
44031	stainless steel	1-1/2" (38 mm)	2-1/8" x 7/8" x 1/4" (54 mm x 22 mm x 6 mm)	.80





All dimensions are in inches and (millimeters).

#### **Pocket Knives – One Blade**

#### Compact Pocket Knives -**Drop Point Blade**

- Compact and lightweight knives.
- Stainless steel handles and blades for long life.



44033

- · Rosewood handle inserts on both sides.
- Modified spearpoint blades lock open.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
44032	stainless steel	1-5/8" (41 mm)	2-1/2" (64 mm)	1.0
44033	stainless steel	2" (51 mm)	3" (76 mm)	1.8
44034	stainless steel	2-5/8" (67 mm)	4" (102 mm)	4.0

#### Sportsman Knives -**Drop Point Blade**

- Curved handle with big bolster.
- Brass bolsters and ebony wood handles.
- Stainless steel blades for long life.
- Brass linings.



- Blade locks open.
- Cat. No. 44037 furnished with leather snap case with belt loop.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
44035	stainless steel	2" (51 mm)	3" (76 mm)	1.5
44036	stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	2.5
44037	stainless steel	3-3/8" (86 mm)	4-7/8" (124 mm)	6.5

#### Pocket Knives - Coping Blade

- Coping-type blade.
- Compact and lightweight.
- Ideal for skinning small wire and cable.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-5	carbon steel	2-1/4" (57mm)	3-1/4" (83mm)	1.5
1550-11*	carbon steel	2-1/4" (57mm)	3-1/4" (83mm)	1.5
1550-14*	carbon steel	3" (76mm)	4-1/4" (108mm)	4.0
1550-45	stainless steel	2-1/4" (57mm)	3-1/4" (83mm)	1.5

<sup>\*</sup>Blade locks open



1550-11

#### Pocket Knives -**Sheepfoot Slitting Blade**

- Extra-large curved sheepfoot slitting-blade -2-5/8" (67 mm) long.
- Ideal for heavy-duty line work.
- Woodgrain plastic handle.
- Blade locks open.



1550-4

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-4	carbon steel	2-5/8" (67 mm)	4" (102 mm)	4.0
1550-44	stainless steel	2-5/8" (67 mm)	4" (102 mm)	4.0

#### **Pocket Knife - Slitting Blade**

- Large, stainless steel, curved-sheepfoot slitting blade - 2-1/2" (64 mm) long.
- Ideal for heavy-duty line work.
- Plastic handle.
- Blade locks open.



1550-24

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-24	stainless steel	2-1/2" (64 mm)	4-3/8" (111 mm)	2.5

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.



#### **Pocket Knives - Two Blades**

# 2-Blade Pocket Knives -Spearpoint and Screwdriver-**Tip Blades**

- Standard spearpoint blade 2-1/2" (64 mm) long.
- Screwdriver-tip blade 2-1/2" (64 mm) long.
- Screwdriver-tip blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-2	carbon steel	2-1/2" (64 mm)	3-3/4" (95 mm)	4.0
1550-42	stainless steel	2-1/2" (64 mm)	3-3/4" (95 mm)	4.0



 Curved sheepfoot slitting blade -2-3/8" (60 mm) long.

1550-2

1550-6

Screwdriver-tip blade – 2-1/2" (64 mm) long.

Screwdriver blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-7	carbon steel	2-3/8" (60 mm) and 2-1/2" (64 mm)	3-3/4" (95 mm)	4.0
		2-1/2" (64 mm)		

#### 2-Blade Pocket Knife – Sheepfoot and Insulation-Slitting Blades

- Curved sheepfoot skinning blade 2-3/8" (60 mm) long.
- Special insulation-slitting blade 1-1/2" (38 mm) long.
- Slitting blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-10	carbon steel	2-3/8" (60 mm) and 1-1/2" (38 mm)	3-3/4" (95 mm)	4.0



1550-7

1550-9

1550-10

# **Pocket Knives - Three Blades**



- Standard spearpoint blade 2-1/2" (64 mm) long.
- Screwdriver-tip blade 2-1/2" (64 mm) long.
- Screwdriver blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-6	carbon steel	2-3/8" (60 mm), 2-1/2" (64 mm), 2-1/2" (64 mm)	3-3/4" (95 mm)	5.0



- Spearpoint blade 2-1/2" (64 mm) long.
- Special insulation-slitting blade 1-1/2" (38 mm) long.
- Screwdriver-tip blade 2-1/2" (64 mm) long.
- Both slitting blade and screwdriver-tip blade lock open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-9	carbon steel	2-1/2" (64 mm), 1-1/2" (38 mm), 2-1/2" (64 mm)	3-3/4" (95 mm)	5.0

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits.



# **Sharpening Tools**

#### **Pocket-Sized Knife Sharpener**

- A rugged, versatile sharpener featuring fine craftsmanship and unique design.
- Blade unscrews and stores in handle for convenient carrying in tool box, pouch, or pocket.
- Blade is precision-cut, hard-chromed steel for accurate, consistent sharpening and long life.
- Magnetized to trap metal particles when sharpening.
- Handle is a high-visibility orange color with handy pocket clip.



44151

Cat. No.	Blade Length	Length Closed	Weight (lbs.)
44151	3-3/4" (95 mm)	5-1/2" (140 mm)	.05

#### **Combination Knife and Scissors Sharpener**

- High-grade, tungsten-carbide inserts sharpen both sides of the blade at the same time.
- Restores knife edge in three or four strokes.
- Built-in finger guard helps to protect your hand.
- Lightweight, compact size for easy carrying and storage.
- Sharpens electrician's scissors, pocket knives, retractable-blade utility knives, razor blade knives and serrated knives.

Cat. No.	Overall Size	Weight (lbs.)
48036	4" L x 2-1/4" W x 3/4" D	.10
	(102 mm x 57 mm x 19 mm)	



**AWARNING:** Improper use of knife and scissors sharpener and/or failure to follow instructions can result in injuries. Keep your fingers behind the curved guard and your thumb securely on the multi-grooved thumb-rest indentation, never in front of it.

# **Utility Knives**

#### Utility Knife — Retractable Blade

- Top button moves heavy-duty, razor-edged blade to any of three cutting positions.
- Double-ended, reversible blade retracts fully for carrying.
- · Lightweight aluminum handle is shaped for comfort.
- Accepts most standard blades.
- Includes three standard blades, stored in handle.
- Blades made in the U.S.A.
- Leather holder available, Cat. No. 5185.

Cat. No.	Length Closed	Weight (lbs.)
44100	6" (152 mm)	.22



44100

#### **Utility Knife Blades**

- Heavy-duty razor-edged blades.
- Universal size fits Klein and most other makes of utility knives.
- Blades are reversible for extra life.
- Blades made in the U.S.A.

Cat. No.	Blade Size	Package Size	Weight (lbs.)
44101	2-7/16" x .025" (62 mm x 6 mm)	5 blades	.05
44104	2-7/16" x .025" (62 mm x 6 mm)	bulk package of 400 blades	4.0



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.





# **Utility Knives**

#### **Auto Loading Folding Retractable Utility Knife**



44130

- Auto-loading blade for faster and safer blade changes.
- High quality triple ground blades stay sharp longer.
- Quick release button for easy blade change.
- · Heavy-duty, durable construction.
- Rubber grips on handle for improved control and comfort.
- Internal blade storage holds and includes 3 blades.

#### **Auto Loading Retractable Utility Knife**



44132

- Auto-loading blade for faster and safer blade changes.
- High quality triple ground blades stay sharp longer.
- Quick release button for easy blade change.
- · Heavy-duty, durable construction.
- Rubber grips on handle for improved control and comfort.
- Internal blade storage holds and includes 3 blades.

Cat. No.	Length Closed	Overall Length w/Blade	Weight
44132	6.25" (158.8 mm)	N/A	.48 lbs. (0.22 kg)

#### Klein Kurve® Retractable Utility Knife




44133

**Blade** 

**Storage** 

- Designed for improved comfort & cutting ability.
- High quality triple ground blades stay sharp longer.
- Quick release button for easy blade change.
- Heavy-duty, durable construction.
- Rubber grips on handle for improved control and comfort.





Cat. No.	Length Closed	Overall Length w/Blade	Weight
44130	4.25" (108 mm)	6.625" (168.3 mm)	.47 lbs. (0.21 kg)

#### **Folding Utility Knife**



44131

- Push button to easily open and close.
- High quality triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- Heavy-duty, durable construction.

Cat. No.	Length Closed	Overall Length w/Blade	Weight
44131	4.125" (104.8 mm)	4.50" (114.3 mm)	.27 lbs. (0.12 kg)

#### **Utility Knife Blade Dispenser**

- 50 blades included.
- High quality triple ground blades stay sharp longer.
- Gauge on dispenser indicates blades remaining.
- Convenient interim storage for used blades.
- Blades are compatible with all standard utility knives.



44103

Cat. No.	Dimensions	Weight
44103	4.33" x 2.80" x 1.30" (71 mm x 32 mm x 110 mm)	1 lb. (0.45 kg)

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits

**AWARNING:** Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

# **Special-Purpose Knives**

#### **Cable-Sheath Splitting Knife**



- · Compact, lightweight knife for opening lead cables.
- Rugged, forged tempered cutlery steel blade.
- Sharp, chisel-shaped edge.
- Hammer head on back.
- Plastic-dipped handle for comfort.
- Leather guard available, Cat. No. 5574S.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
1515-S	7-3/8" (187 mm)	2-19/32" (66 mm)	.35

#### **Cable/Lineman's Skinning Knives**



- Three-inch steel blade withstands frequent scoring and slitting of cable jacket.
- Blade and ring are securely molded in handle.
- Notch on blade back for scraping or removing wire insulation.
- Comfortable textured handle with finger grooves and guard.
- No contact between stainless steel ring and hardened steel blade (Cat. No. 1570-3).
- Rectangle-shaped handle design for attachment to some utility hot stick equipment.
- Leather sheath available, Cat. No. 5163.

Cat. No.	Description	Handle Color	Length Less Ring	Weight (lbs.)
1570-3	hook blade, notch, and ring	black	8" (203 mm)	.30
1570-3LR	hook blade and notch	black	8" (203 mm)	.29

#### Cable-Splicer's Knife



- Special-purpose short blade with comfortable, full-sized, heavy-duty handle.
- Coping-type blade made of the finest cutlery steel, tough and carefully tempered to hold its edge.
- Handle is textured for comfort and firm grip.
- Hang hole for easy storage and portability.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
44200	6-1/4" (159 mm)	1-3/4" (44 mm)	.15

#### Bell System Cable-Sheath Splitting Knife — Heavy-Duty



- Heavy-duty knife for splitting cable sheaths.
- Rugged, forged tempered cutlery steel blade.
- Sharp chisel-shaped edge.
- Plastic-dipped handle for comfort.
- Leather guard available, Cat. No. 5574L.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
1515-1	8-3/4" (222 mm)	4-1/2" (114 mm)	1.20

#### **Cable-Splicer's Kits**



- Cuts cable, telephone wire, and strips insulation.
- Dimensions: 2-1/8" x 7-1/2" (54 mm x 191 mm).

46037

bs.)

Kit Contai	ns	Weight (II
cable splicer's kit		.50
Cat. No.	Description	
44200	cable-splicer's knife	_
2100-7 electrician's scissors with stripping notches		-
5187	slotted leather holder for belts up to 2" (51 mm) wide	_
	<b>Cat. No.</b> 44200 2100-7	Cat. No.     Description       44200     cable-splicer's knife       2100-7     electrician's scissors with stripping notches       5187     slotted leather holder for belts

Cat. No.	Kit Contains		Weight (lbs.)
46039	cable splicer's kit - with free-fall snip		.58
	Cat. No.	Description	
	44200	cable-splicer's knife	
	2101-0 free-fall snip		
	5187	slotted leather holder for belts up to 2" (51 mm) wide	-

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.





#### **Electrician's Scissors**

# Electrician's Scissors

- Designed for telecom and electrical applications and heavy-duty use.
- Strong, tough tempered steel.
- Nickel-plated finish resists corrosion.
- Scraper and file on outside of both blades.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-5	5-1/4" (133 mm)	1-7/8" (48 mm)	.20



- Upper blade has notches for stripping 19 AWG and 23 AWG wire.
- Designed for telecom and electrical applications and heavy-duty use.
- Strong, tough tempered steel.
- Nickel-plated finish resists corrosion.
- Scraper and file on outside of both blades.
- Serrated, lower blade reduces slippage.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-7	5-1/4" (133 mm)	1-7/8" (48 mm)	.20



- Stainless steel blades to maintain blade durability and sharpness.
- Blade is fully serrated for non-slip cutting action.
- Free-fall snip feature for ease of use (2100-8).
- Cuts electrical communication 19 AWG and 23 AWG wire.
- Extended handle provides comfort and cutting leverage for wire cutting application (2100-8).
- 56 HRC.

2100-5

2100-7

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-8	6-5/16" (160 mm)	1-7/8" (48 mm)	.21
2100-9	5-1/4" (133 mm)	1-7/8" (48 mm)	.21

# **Industrial High-Leverage Shears**



All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.





# **Industrial Utility Snips**



 Nickel chrome plating resists corrosion and rusting.

- One blade is serrated for non-slip cutting action.
- Spring loaded for self-opening action.
- Handy closure lock for convenient storage (24000, 24001).
- Compatible for right- and left-handed users.
- Excellent for cutting Kevlar® insulation in fiber optic applications (24000, 24001).
- Excellent for cutting electronics and filaments (24005).

Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company.



Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
24000	6-1/2" (165 mm)	5/8" (16 mm)	.28
24001	6-1/2" (165 mm)	1" (25 mm)	.28
24005	5" (127 mm)	1" (25 mm)	.22

#### **Bent Trimmers**



24000

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
23008	9" (229 mm)	3-1/2" (89 mm)	.41
23010	10-1/2" (267 mm)	4-1/2" (114 mm)	.99
23011	11-1/4" (286 mm)	4-3/4" (121 mm)	1.24
23015	9-3/4" (248 mm)	3-3/16" (81 mm)	.94

**Single Serrated Blunt Blade Shear** 

- Cuts belting, abrasive belting, heavy fabric, leather, upholstery and heavy carpet.
- Deep serrated blade for non-slip cutting action.

All dimensions are in inches and (millimeters).

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Never use on or near live electrical circuits.



#### **Hammers**

#### **Electrician's Straight-Claw Hammer**



- to protect neck from fraying and splintering if incorrectly struck or overstruck.

  High-strength fiberglass shaft absorbs shock and keeps
- head tight.Comfortable, perforated neoprene grip bonded to handle.
- Extra-long neck and narrow striking face are ideal for reaching into outlet boxes and other tight areas.
- Balanced and designed specifically for use in electrical work.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
807-18	18 oz. (510 g)	15" (381 mm)	1.85

#### **Curved-Claw Hammers — Heavy-Duty**



- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Curved claw gives maximum nail-pulling leverage.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
818-16	16 oz. (454 g)	13" (330 mm)	1.85
818-20	20 oz. (567 g)	14" (356 mm)	2.00

#### **Lineman's Straight-Claw Hammer**



- Heavy-duty, double-duty hammer drives lags and pulls large nails.
- Special high-carbon steel head with solid, octagon-shaped driving end and thick, strong claw.
- Straight-grain hickory handle, lacquered to withstand weather.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
832-32	32 oz. (907 g)	15" (381 mm)	2.50

#### Straight-Claw Hammers — Heavy-Duty



 Durable plastic-alloy jacketing helps to protect neck from fraying and splintering if incorrectly struck or overstruck.

- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Straight-claw design for easy nail pulling in tight quarters.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
808-16	16 oz. (454 g)	13" (330 mm)	1.85
808-20	20 oz. (567 g)	14" (356 mm)	2.00

#### **Ball-Peen Hammers**



- Crowned face with uniform bevel.
- Smoothly rounded peen.
- Straight-grain hickory handle is stained and lacquered to withstand weather.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
803-8	8 oz. (227 g)	11-1/2" (292 mm)	.75
803-12	12 oz. (340 g)	12-1/2" (318 mm)	1.10
803-16	16 oz. (454 g)	13-1/2" (343 mm)	1.40
803-24	24 oz. (680 g)	15" (381 mm)	1.90
803-32	32 oz. (907 g)	15" (381 mm)	2.50

#### **Hand-Drilling Hammer**



- Extra-heavy, forged steel head, hardened and tempered.
- Short handle for working in close quarters.
- Select hickory handle, triple-wedged and lacquered to withstand weather.
- Special handle treatment removes handle moisture and replaces it with oil to help eliminate the effects of extreme temperatures.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
823-48	48 oz. (1361 g)	10" (254 mm)	3.25

All dimensions are in inches and (millimeters) unless otherwise specified.

For Sledge, Brass, Copper + Normalized Hammers, see Mining Tools section

**AWARNING:** Always wear approved eye protection.

#### Hammers

#### Lineman's Double-Face Hammer



- Designed for pole-line work.
- Rugged and well-balanced, with the weight to drive lag bolts.
- Forged, tempered-steel head is only 3-3/4" (95 mm) long for use in tight areas.
- Identical faces with 1-3/4" (44 mm) round-crown driving surface and beveled edges.



both sides

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
809-36	36 oz. (1021 g)	14" (356 mm)	2.50

#### **Lineman's Milled-Face Hammer**



- One milled face for driving staples used in pole-line work and common, unhardened nails.
- Other face is smooth for driving heavier duty hardware.
- Rugged and well-balanced, with the weight to drive lag bolts.
- Forged, tempered-steel head is only 3-3/4" (95 mm) long for use in tight areas.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
809-36MF	36 oz. (1021 g)	14" (356 mm)	2.50

## **Setting Hammer**



- Durable epoxy resin handle helps to protect neck from fraying and splintering if incorrectly struck or over struck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Cushioned, PVC grip bonded to handle.
- Special high-carbon steel, octagon-shaped head with flat striking surface and rounded cross peen.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
820-16	16 oz. (454 g)	13" (330 mm)	1.6

#### **Riveting Hammer**



- Forged high-carbon steel round head is hardened for additional durability.
- Flat striking surface with rounded cross peen.
- Straight-grain American hickory handle is stained and lacquered.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
821-12	12 oz. (340 g)	12-1/4" (311 mm)	1.1

#### **Dead Blow Hammers**



When struck, the shot directs the striking power and increases the impact, creating a dead blow effect.

> The reduced rebound upon impact transfers full energy of the blow to the object

being struck.

- Durable, abrasion resistant non-marring hammer face.
- Increased striking force with zero impact rebound.
- Design isolates user from striking impact and reduces fatigue.
- 40% more driving power than other dead blow hammers.
- Protects job surface from damage.
- Applications: HVAC, metal fabrication, electronics, oil and mining, wood and metal assembly, automotive, aerospace.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
811-16	16 oz. (454 g)	12.5" (318 mm)	1.44
811-32	32 oz. (908 g)	18" (457 mm)	1.8

All dimensions are in inches and (millimeters) unless otherwise specified.





- Heat-treated, high-carbon steel for necessary hardness and durability.
- Cuts, shapes and removes metal.
- Corrosion-resistant black finish.

Cat. No.	Blade Width	Overall Length	Weight (lbs.)
66140	3/8" (10 mm)	5" (127 mm)	.10
66142	1/2" (13 mm)	6" (152 mm)	.20
66143	5/8" (16 mm)	6-1/2" (165 mm)	.35
66144	3/4" (19 mm)	7-1/2" (191 mm)	.60
66145	7/8" (22 mm)	8" (203 mm)	.85
66146	1" (25 mm)	8-1/2" (216 mm)	1.31

 Heat-treated, high-carbon steel for necessary hardness and durability.

Cold Chisels — Long-Length

- Cuts, shapes and removes metal.
- Accurately ground edge and long length work better in hard-to-reach areas.
- Corrosion-resistant black finish.

Cat. No.	Blade Width	Overall Length	Weight (lbs.)
66174	1/2" (13 mm)	12" (305 mm)	.40
66177	3/4" (19 mm)	12" (305 mm)	1.05
66183	1" (25 mm)	12" (305 mm)	2.05

#### **Electrician's Chisel**



- One-piece handle and blade forged of strong alloy steel.
- Corrosion-resistant black finish extends to the polished blade edge.

Cat. No.	Blade Width	Overall Length	Weight (lbs.)
66100	2-3/4" (70 mm)	8" (203 mm)	1.10

#### **Punches**

#### **Drift Punches**

- High-carbon steel for durability.
- Rugged design for impact strength.
- Strong, heat-treated points are smooth and precision tapered. Corrosion-resistant black finish.

Point	Taper	Overall Length	Weight (lbs.)
1/8" (3 mm)	4-1/4" (108 mm)	8" (203 mm)	.20
3/16" (5 mm)	5" (127 mm)	9" (229 mm)	.35
1/4" (6 mm)	5-1/2" (140 mm)	11" (279 mm)	.75
5/16" (8 mm)	5-1/2" (140 mm)	11" (279 mm)	.75
	1/8" (3 mm) 3/16" (5 mm) 1/4" (6 mm)	1/8" (3 mm) 4-1/4" (108 mm) 3/16" (5 mm) 5" (127 mm) 1/4" (6 mm) 5-1/2" (140 mm)	1/8" (3 mm)     4-1/4" (108 mm)     8" (203 mm)       3/16" (5 mm)     5" (127 mm)     9" (229 mm)       1/4" (6 mm)     5-1/2" (140 mm)     11" (279 mm)

#### **Center Punches**



- High-carbon steel for durability.
- Rugged design for impact strength.
- Smooth-ground points heat-treated to stay sharp and true longer.
- Corrosion-resistant black finish.

Cat. No.	Shank Diameter	Overall Length	Weight (lbs.)
66310	1/4" (6 mm)	4 1/4" (108 mm)	.05
66311	5/16" (8 mm)	4 1/2" (114 mm)	.10
66312	3/8" (10 mm)	5" (127 mm)	.10
66313	1/2" (13 mm)	6" (152 mm)	.25

#### **Pin Punches**

- High-carbon steel for durability.
- 66324

66343

Precision-ground shank.

- Heat-treated for added strength and hardness at working end.
- Corrosion-resistant black finish.

Cat. No.	Point Diameter	Overall Length	Weight (lbs.)
66320	1/16" (1.5 mm)	4-1/4" (108 mm)	.05
66321	3/32" (2 mm)	4-3/4" (121 mm)	.10
66322	1/8" (3 mm)	5" (127 mm)	.10
66323	5/32" (4 mm)	5-1/4" (133 mm)	.10
66324	3/16" (5 mm)	5-1/2" (140 mm)	.10
66325	1/4" (6 mm)	7" (178 mm)	.20






#### **USA Made Professional Series Multimeters**

- True RMS for accurate readings of all signals.
- Low impedance reduces ghost voltage.
- Enhanced basic DC accuracy.
- Bar graph responds quickly to changes in measurement.



#### Additional Features for Cat. No. MM6000

- Max / Min / Relative reading for quick troubleshooting in the field.
- Measures frequency, duty cycle, temperature, and capacitance.
- Lead warning indicates when test leads are not properly connected.







Suggested accessories for Cat. Nos. MM5000 & MM6000

• Magnetic hanger kit (Cat. No. 69190)





Measurement		MM5000/ MM5000N* Electrician's TRMS Multimeter	MM6000/ MM6000N* Electrician's / HVAC TRMS Multimeter
AC Current	Ã	_	10A
DC Current	Ā	_	10A
AC Voltage	v	1000V	1000V
DC Voltage	Ÿ	1000V	1000V
Audible Continuity	01))	•	•
Resistance Range	Ω	40M <b>Ω</b>	50M $\Omega$
Data Hold	HOLD	•	•
Diode Test	<b>—</b>	•	•
Protective Boot		•	•
Lead Storage		•	•
Auto Power Off	Apo	•	•
Back Light	;\ <del>\</del> <	•	•
Auto Ranging	AUT0	•	•
Temperature	°F °C	_	-58~1832°F -50~1000°C
uA Setting	$\overline{\widetilde{\mu A}}$	•	•
Capacitance	<b>⊣</b> (	_	6000μF
Range Hold	RANGE	•	•
Frequency	Hz	_	399.9kHz
Max/Min	MAX/MIN	•	•
Duty Cycle	%	_	•
Relative Reading	Δ	_	•
Optional Hanger Kit		•	•
Bar Graph	liml	•	•
Lead Warning		_	•
Auto Hold	A-HOLD	•	•
True RMS	TRMS	•	•
Low Impedance	LOW Z	•	•
Ingress Protection	::: <b>:</b>	IP40	IP20
Drop Protection	4	3m (10 ft)	3m (10 ft)
Safety Rating	A	CAT IV 600V	CAT IV 600V
Basic DC Accuracy		±0.3%	±0.2%
Counts	00.00	4000	6000
Listings		LISTED	CLISTED

4007036





#### **Professional Series Multimeters**

- Measures continuity, resistance and voltage.
- Data Hold feature saves measurement for later viewing.
- Audible continuity indicator.
- Lead storage.

#### Additional features for MM500:

- User-friendly three button design.
- IP67 dust and water proof.
- 10 foot / 3 meter drop protection.
- CAT IV safety rating for 600V.









Measurement		MM100 Manual Ranging Multimeter	<b>MM200</b> Auto Ranging Multimeter	MM500 Auto Ranging Multimeter
AC Current	$\widetilde{A}$	<del>_</del>	10A	_
DC Current	Ā	10A	10A	_
AC Voltage	ĩ	600V	600V	750V
DC Voltage	Ψ̈	600V	600V	750V
Audible Continuity	01))	•	•	•
Resistance Range	Ω	2М $\Omega$	40M $\Omega$	4000Ω
Battery Test	- +3 Test	•	_	_
Data Hold	HOLD	•	•	_
Diode Test	<b>→</b> ⊢	•	•	_
Protective Boot		•	•	_
Lead Storage	-	•	•	•
Auto Power Off	Apo	_	•	•
Back Light	> <b>/</b> <	_	•	•
Auto Ranging	AUTO	_	•	•
Temperature	°F °C	_	-4~1832°F	_
uA Setting	$\widetilde{\widetilde{\mu A}}$	_	•	_
Capacitance	46	_	200μF	_
Range Hold	RANGE		•	_
Frequency	Hz	_	1MHz	_
Max/Min	MAX/MIN	_	<u> </u>	_
Duty Cycle	%	_	_	_
Relative Reading	Δ	_	_	_
Optional Hanger Kit		_	_	_
Bar Graph	liiil	_	_	_
Lead Warning		_	_	_
Auto Hold	A-HOLD	_	_	•
True RMS	TRMS	_	<u> </u>	_
Low Impedance	LOW Z	_	_	_
Ingress Protection	::: <b>::</b>   =	_	_	IP67
Drop Protection	<b>\(\begin{array}{c}\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\</b>	1m (3 ft)	1m (3 ft)	3m (10 ft)
Safety Rating	A	CAT III 600V	CAT III 600V	CAT IV 600V
Basic DC Accuracy		±0.5%	±0.5%	±0.5%
Counts	00.00	2000	4000	4000
Listings		ce LISTED Us C €	c∰us <b>C €</b>	C UL US LISTED

3194551

3194551

45ZK

#### Professional Series Multimeters Continued

\*A NIST certified product is guaranteed to have been specially tested to ensure its accuracy. NIST certified meters are special order (lead time: 7 business days). NIST certifications are good for one year from the date of calibration.









Measurement		MM1000/ MM1000N* Electrician's / HVAC Multimeter	MM1300/ MM1300N* Electrician's / HVAC Multimeter	MM2000/ MM2000N* Electrician's / HVAC TRMS Multimeter	MM2300/ MM2300N* Electrician's / HVAC TRMS Multimeter
AC Current	$\widetilde{A}$	10A	10A	10A	10A
DC Current	Ā	10A	10A	10A	10A
AC Voltage	v	1000V	1000V	1000V	1000V
DC Voltage	Ÿ	1000V	1000V	1000V	1000V
Audible Continuity	01))	•	•	•	•
Resistance Range	Ω	40M <b>Ω</b>	60М $\Omega$	40M $\Omega$	60M <b>Ω</b>
Data Hold	HOLD	•	•	•	•
Diode Test	<b>→</b>	•	•	•	•
Protective Boot		•	•	•	•
Lead Storage		•	•	•	•
Auto Power Off	Apo	•	•	•	•
Back Light	> <b>\</b> <	•	•	•	•
Auto Ranging	AUTO	•	•	•	•
Temperature	°F °C	-58~1832°F -50~1000°C	-58~1832°F -50~1000°C	-58~1832°F -50~1000°C	-58~1832°F -50~1000°C
uA Setting	$\overline{\widetilde{\mu A}}$	•	•	•	•
Capacitance	<del>-</del> 16	4000μF	6000μF	4000μF	6000μF
Range Hold	RANGE	•	•	•	•
Frequency	Hz	499.9kHz	499.9kHz	499.9kHz	499.9kHz
Max/Min	MAX/MIN	•	•	•	•
Duty Cycle	%	•	•	•	•
Relative Reading	Δ	•	•	•	•
Optional Hanger Kit		•	•	•	•
Bar Graph	liml	•	•	•	•
Lead Warning	<b>→</b>	_	•	_	•
Auto Hold	A-HOLD	_	•	_	•
True RMS	TRMS	_	_	•	•
Low Impedance	LOW Z	_	_	•	•
Ingress Protection	<b>::::</b>	IP20	IP20	IP20	IP20
Drop Protection		2m (6 ft)	2m (6 ft)	2m (6 ft)	2m (6 ft)
Safety Rating	A	CAT IV 600V	CAT IV 600V	CAT IV 600V	CAT IV 600V
Basic DC Accuracy		±0.5%	±0.5%	±0.5%	±0.5%
Counts	00.00	4000	6000	4000	6000
Listings		C UL US	C UL US	C UL US	C UL US
		45ZK	45ZK	45ZK	45ZK

#### **Multimeter Specifications**

Cat. No.	NIST certified	CAT Rating	Batteries	Height	Width	Depth	Weight	Included Accessories
MM100	_	CAT III 600V	1 x 9V	5.75" (146 mm)	2.75" (70 mm)	1.75" (45 mm)	8.0 oz. (227 g)	test leads
MM200	_	CAT III 600V	1 x 9V	5.75" (146 mm)	2.75" (70 mm)	1.75" (45 mm)	8.2 oz. (232 g)	test leads thermocouple
MM500	_	CAT IV 600V	2 x AAA	5.75" (146 mm)	2.75" (70 mm)	1.75" (45 mm)	8.0 oz. (227 g)	test leads <b>NEW!</b>
MM1000	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple
MM1000N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple
MM1300	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case
MM1300N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case
MM2000	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple
MM2000N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple
MM2300	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case
MM2300N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case
MM5000	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, case
MM5000N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, case
MM6000	_	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case
MM6000N	yes	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (89 mm)	1.875" (48 mm)	14.0 oz. (397 g)	test leads, thermocouple, case

#### **Multimeter Replacement Fuses**



69192

Cat. No.	For Use With	Fuse Type
69191	MM1000, MM1300, MM2000, MM2300, MM6000	F 11A / 1000V
69192	MM1000, MM1300, MM2000, MM2300, MM6000	F 440mA / 1000V
69193	MM100 Fuse Kit	F10A / 500V, F250mA / 250V
69194	MM200 Fuse Kit	F10A / 500V, F400mA / 250V

#### AWARNINGS:

To ensure safe operation and service of the tester, follow these instructions. Failure to observe these warnings can result in severe injury or death.

- Before each use, verify meter operation by measuring a known voltage or current.
- Never use the meter on a circuit with voltages that exceed the category based rating of this meter.
- · Do not use the meter during electrical storms, or in wet weather.
- . Do not use the meter or test leads if they appear to be damaged.
- Ensure meter leads are fully seated, and keep fingers away from the metal probe contacts when making measurements.
- Do not open the meter to replace batteries while the probes are connected.
- Use caution when working with voltages above 60V DC, or 25V AC RMS. Such voltages pose a shock hazard.
- To avoid false readings that can lead to electrical shock, replace batteries if a low battery indicator appears.
- Unless measuring voltage or current, shut off and lock out power before measuring resistance or capacitance.
- Always adhere to local and national safety codes. Use individual protective equipment to prevent shock and arc blast injury where hazardous live conductors are exposed.

# **Clamp Meters**

#### Professional Series Clamp Meters

- Large jaw sizes.
- Worklights illuminate dark work spaces.
- Data hold captures measurements in any situation.

# Additional Features for Cat. Nos. CL1000, CL1200, CL1300

- Built-in magnetic mount for hands-free convenience.
- Non-contact voltage detection at the push of a button.
- Quick-response bar graph shows elusive fluctuations.



Measurement		<b>CL100</b> 600A AC Clamp Meter	<b>CL200</b> 600A AC Clamp Meter w/ Temp	CL1000/CL1000N* 400A AC Clamp Meter	CL1200/CL1200N* 600A AC Clamp Meter	CL1300/CL1300N 600A AC Clamp Meter w/ Temp
AC Current	$\widetilde{A}$	600A	600A	400A	600A	600A
DC Current	Ā	_	_	_	_	_
AC Voltage	v	600V	600V	750V	750V	750V
DC Voltage	Ÿ	600V	600V	1000V	1000V	1000V
Audible Continuity	01))	•	•	•	•	•
Resistance Range	Ω	20ΜΩ	40M <b>Ω</b>	40M <b>Ω</b>	60M <b>Ω</b>	60M <b>Ω</b>
Data Hold	HOLD	•	•	•	•	•
Auto Power Off	Apo	•	•	•	•	•
Diode Test	<b>-</b>	•	•	•	•	•
Back Light	> <b>\</b> <	•	•	•	•	•
Work/Clamp Light	<b>-</b>	•	•	•	•	•
Frequency	Hz	_	100kHz	499.9kHz	499.9kHz	499.9kHz
Capacitance	-16	_	100μF	4000μF	6000μF	6000µF
Duty Cycle	%	_	•	•	•	•
Temperature	°F °C	_	-4~1832°F -20~1000°C	_	_	-22~752°F -30~1000°C
Non-Contact Voltage Test	NCV	_	_	•	•	•
Max/Min	MAX/MIN	Max	_	•	•	•
µA Setting	$\overline{\widetilde{\mu A}}$	_	•	•	•	•
Rel/Zero	Δ	_	_	_	•	•
Magnetic Mount	C	_	_	•	•	•
Bar Graph	liiiil	_	_	•	•	•
True RMS	TRMS	_	_	_	_	_
Low Impedance	LOW Z	_	_	_	_	_
Ingress Protection		_	_	_	IP42	IP42
Drop Protection	<b>\</b>	1m (3 ft)	1m (3 ft)	1m (3 ft)	2m (6 ft)	2m (6 ft)
Safety Rating	Â	CAT III 600V	CAT III 600V	CAT III 600V	CAT IV 600V	CAT IV 600V
Counts	00.00	2000	4000	4000	6000	6000
Listings		c∰us <b>C</b> €	celus c∈	C UL US	C UL US	C UL US
		3194551	3194551	45ZK	45ZK	45ZK



#### Professional Series Clamp Meters Cont.

Additional Features for Cat. Nos. CL2000, CL2200, CL2300, CL2500

- Built-in magnetic mount for hands-free convenience.
- Non-contact voltage detection at the push of a button.
- Quick-response bar graph shows elusive fluctuations.

\*A NIST certified product is guaranteed to have been specially tested to ensure its accuracy. NIST certified meters are special order (lead time: 7 business days). NIST certifications are good for one year from the date of calibration.









45ZK

Measurement		CL2000/CL2000N* 400A AC/DC TRMS Clamp Meter	CL2200/ CL2200N* 600A AC/DC TRMS Clamp Meter	CL2300/ CL2300N* 600A AC/DC TRMS Clamp Meter w/ Temp	CL2500/ CL2500N* 1000A AC/DC TRMS Clamp Meter
AC Current	Ã	400A	600A	600A	1000A
DC Current	Ā	400A	600A	600A	1000A
AC Voltage	v	750V	750V	750V	750V
DC Voltage	Ÿ	1000V	1000V	1000V	1000V
Audible Continuity	01))	•	•	•	•
Resistance Range	Ω	40M <b>Ω</b>	60M <b>Ω</b>	60М $\Omega$	60М $\Omega$
Data Hold	HOLD	•	•	•	•
Auto Power Off	Apo	•	•	•	•
Diode Test	<b>→</b>	•	•	•	•
Back Light	`\r\`	•	•	•	•
Work/Clamp Light		•	•	•	•
Frequency	Hz	499.9kHz	499.9kHz	499.9kHz	499.9kHz
Capacitance	46	4000μF	6000μF	6000μF	6000μF
Duty Cycle	%	•	•	•	•
Temperature	°F °C	_	_	-22~752°F -30~400°C	_
Non-Contact Voltage Test	NCV	•	•	•	•
Max/Min	MAX/MIN	•	•	•	•
μA Setting	$\widetilde{\widetilde{\mu A}}$	•	•	•	•
Rel/Zero	Δ	•	•	•	•
Magnetic Mount	C	•	•	•	•
Bar Graph	liiil	•	•	•	•
True RMS	TRMS	•	•	•	•
Low Impedance	LOW Z	_	_	_	_
Ingress Protection	<b>:</b>	_	IP42	IP42	IP42
Drop Protection	<b>\(\begin{array}{c}\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\</b>	1m (3 ft)	2m (6 ft)	2m (6 ft)	1m (3 ft)
Safety Rating	A	CAT III 600V	CAT IV 600V	CAT IV 600V	CAT IV 600V
Counts	00.00	4000	6000	6000	6000
Listings		C UL US	C UL US	C (UL) US LISTED	C UL US

45ZK

45ZK

45ZK



# **Clamp Meters**

#### **Clamp Meter Specifications**

Cat. No.	CAT Rating	Batteries	Jaw Size	Height	Width	Depth	Weight	Included Accessories
CL100	CAT III 600V	3 x AAA	1.0" (25 mm)	8.2" (208 mm)	3.0" (76 mm)	1.4" (36 mm)	9.9 oz. (281 g)	test leads, case
CL200	CAT III 600V	3 x AAA	1.0" (25 mm)	8.2" (208 mm)	3.0" (76 mm)	1.4" (36 mm)	10.0 oz. (283 g)	test leads, case, thermocouple
CL1000	CAT III 600V	2 x AAA	1.25" (32 mm)	8.875" (225 mm)	3.375" (86 mm)	1.5" (38 mm)	10.7 oz. (303 g)	test leads, case
CL1200	CAT III 600V	2 x AAA	1.25" (32 mm)	7.65" (194 mm)	2.56" (65 mm)	1.38" (35 mm)	11.9 oz. (337 g)	test leads, case
CL1300	CAT III 600V	2 x AAA	1.25" (32 mm)	7.65" (194 mm)	2.56" (65 mm)	1.38" (35 mm)	11.9 oz. (337 g)	test leads, case, thermocouple
CL2000	CAT III 600V	2 x AAA	1.25" (32 mm)	8.875" (225 mm)	3.375" (86 mm)	1.5" (38 mm)	10.7 oz. (303 g)	test leads, case
CL2200	CAT III 600V	2 x AAA	1.25" (32 mm)	7.65" (194 mm)	2.56" (65 mm)	1.38" (35 mm)	11.9 oz. (337 g)	test leads, case
CL2300	CAT III 600V	2 x AAA	1.25" (32 mm)	7.65" (194 mm)	2.56" (65 mm)	1.38" (35 mm)	11.9 oz. (337 g)	test leads, case, thermocouple
CL2500	CAT IV 600V	2 x AAA	1.97" (50 mm)	8.09" (205 mm)	2.56" (65 mm)	1.38" (35 mm)	13.6 oz. (386 g)	test leads, case



#### AWARNINGS:

To ensure safe operation and service of the tester, follow these instructions. Failure to observe these warnings can result in severe injury or death.

- · Before each use, verify meter operation by measuring a known voltage or current.
- · Never use the meter on a circuit with voltages that exceed the category based rating of this meter.
- Do not use the meter during electrical storms, or in wet weather.
- Do not use the meter or test leads if they appear to be damaged.
- Ensure meter leads are fully seated, and keep fingers away from the metal probe contacts when making measurements.
- Do not open the meter to replace batteries while the probes are connected.
- Use caution when working with voltages above 60V DC, or 25V AC RMS. Such voltages pose a shock hazard.
- $\bullet \ \ \, \text{To avoid false readings that can lead to electrical shock, replace batteries if a low battery indicator appears.}$
- Unless measuring voltage or current, shut off and lock out power before measuring resistance or capacitance.
- Always adhere to local and national safety codes. Use individual protective equipment to prevent shock and arc blast injury where hazardous live conductors are exposed.





# **Specialty Clamp Meters**

#### **200A AC Fork Meter**

- Open jaw conveniently measures 1/0 wire and AC currents up to 200A. Cat. No. CL3200 measures 3/0 wire.
- Backlit display is readable even in dark locations.
- Relative reading feature automatically calculates the difference between the live measurement and a previously stored measurement.



\*A NIST certified product is guaranteed to have been specially tested to ensure its accuracy. NIST certified meters are special order (lead time: 7 business days). NIST certifications are good for one year from the date of calibration.







#### **200A AC Hook Meter**

- Unique hook-style current clamp fits into tight spaces and measures 1/0 wire.
- Automatically selects voltage or current based on what is being measured. No manual switching between current and voltage required.
- Bright white LED worklight illuminates any workspace.



Measuremen	t	<b>CL3000</b> 200A AC Fork Meter	<b>CL3100</b> 200A AC Hook Meter	CL3200/ CL3200N* 200A AC Fork Meter
AC Current	$\widetilde{A}$	200A	200A	200A
AC Voltage	v	750V	750V	750V
DC Voltage	V	1000V	1000V	1000V
Resistance	Ω	40ΜΩ	40ΜΩ	40ΜΩ
Capacitance	46	40μF	_	_
Frequency / Duty Cycle	Hz%	100kHz	_	_
Diode Test	<b>→</b> ⊢	•	_	_
Continuity	101	•	•	•
Accepts Wire		1/0	1/0	3/0
Non Contact Voltage	NCV	_	_	•
Data Hold	HOLD	•	_	•
Relative Reading	Δ	•	_	_
Auto Power-Off	Apo	•	•	•
Auto Range	RANGE	•	•	•
Backlight	<b>\</b>	•	•	•
Worklight		_	•	•
Voltage / Current Auto Select	RuŁo	_	•	•
Max/Min	MAX/MIN	_	•	_
Bar Graph	liml	<u> </u>	•	•
Magnetic Hanger		_	•	•
Low Impedance	LOW <del>Z</del>	_	_	•
Ingress Protection		_	_	IP30
Drop Protection		1m (3 ft)	1m (3 ft)	2m (6 ft)
Safety Rating	A	CAT III 600V	CAT IV 600V	CAT IV 600V
Display Counts	00.00	4000	4000	4000
Listings		ce c	C UL US	C UL US

NIST certified **CAT Rating Batteries Jaw Size** 

Width Weight **Included Accessories** CL3000 CAT III 600V 1 x 9V 0.5" (13 mm) 7.50" (191 mm) 2.70" (69 mm) 1.70" (43 mm) 7.4 oz. (210 g) test leads, case CL3100 CAT IV 600V 2 x AAA 0.5" (13 mm) 10.25" (260 mm) 2.50" (64 mm) 1.50" (38 mm) 8.6 oz. (244 g) test leads, case CL3200 CAT IV 600V 2 x AAA 0.63" (16 mm) 7.06" (179 mm) 2.56" (65 mm) 1.34" (34 mm) 7.9 oz. (224 g) test leads, case CL3200N3 CAT IV 600V 2 x AAA 0.63" (16 mm) 7.06" (179 mm) 2.56" (65 mm) 1.34" (34 mm) 7.9 oz. (224 g) test leads, case

45ZK

45ZK

# **Electrical Testers**

#### **Electronic Voltage Testers**

- Measures AC and DC voltage at nine common levels up to 600V.
- Probe wires with wear indicators built in.
- Bright LEDs indicate voltage reading without batteries installed.
- Low impedance input reduces possibility of ghost voltages.
- Permanently secured test leads are always there when they are needed.
- Molded lead holders are perfect for easy measurements of tamper-proof outlets.
- Vibration and sound alerts for dangerous voltage levels.
- Modern solid-state construction provides CAT IV 600V safety rating.

#### Additional Features for Cat. No. ET200

- Bright worklight to illuminate your work space.
- Audible continuity.







Cat. No.	CAT Rating	Batteries	Height	Width	Depth	Weight
ET100	CAT IV 600V	3 x AAA	7.375" (187 mm)	2.375" (60.3 mm)	1.25" (31.8 mm)	8.1 oz. (230 g)
ET200	CAT IV 600V	3 x AAA	7.375" (187 mm)	2.375" (60.3 mm)	1.25" (31.8 mm)	8.1 oz. (230 g)

#### **Digital Circuit Breaker Finder**

- Quickly, accurately, and automatically find the correct circuit breaker of any standard 120V outlet.
- Does not require interruption of service. Power can be left on.
- Bright green arrow and loud beeping tone provide clear indication of correct breaker.
- Strong transmitter reaches distances up to 1000 feet.
- Find breakers of light fixtures and bare wires with optional adapter set (Cat. No. 69411, see accessories page).







ET300



Cat. No.		Batteries	Height	Width	Depth	Weight
ET300	receiver	1 x 9V	6.00" (152 mm)	2.00" (50.8 mm)	0.90" (22.9 mm)	3.2 oz. (90.7 g)
	transmitter	N/A	2.80" (71.1 mm)	1.90" (48.3 mm)	1.20" (30.5 mm)	1.6 oz. (45.4 g)



#### **Electrical Testers**

#### Non-Contact Voltage Testers (NCVT-1/NCVT-2)



- High intensity, bright green LED indicates the tester is operational and aids in illuminating the workspace.
- Digitally controlled ON/OFF power button.
- Auto power-off feature conserves and extends battery life.
- Microprocessor controlled low-battery indicator.
- CAT IV 1000 Volt rating provides expanded operation and protection.
- Lightweight, durable polycarbonate plastic resin construction with a convenient pocket-clip.
- Package contains insert card w/ integrated owner's manual and two AAA 1.5 volt batteries.

#### Additional Features for Dual Range NCVT-2

- Automatically detects and indicates low voltage (12-48 Volts AC) and standard voltage (48-1000 Volts AC), allowing broad application.
- Non-contact detection of low-voltage in security, entertainment, communications, environmental control, and irrigation systems.

Voltage Range	12 TO 48 VOLTS AC (Low) (NCVT-2 only)	48 TO 1000 VOLTS AC (Standard)
Audible	low-pitched pulsing beeping sound	high-pitched continuous beeping sound
Visual	blue LED turns off and red LED blinks (approximately 2-times per second).	green LED turns off and red LED illuminates continuously.













Cat. No.	Voltage Range	Frequency Range	Pollution Degree	Batteries	Overall Length	Width	Height	Weight (oz.)	Weight w/ Batteries (oz.)
NCVT-1	48-1000 volts AC	50-500 Hz	2	2 x AAA	5.50" (140 mm)	0.72" (18 mm)	1.0" (25 mm)	0.8 oz. (23 g)	1.6 (46 g)
NCVT-2	12-1000 volts AC	50-500 Hz	2	2 x AAA	5.50" (140 mm)	0.72" (18 mm)	1.0" (25 mm)	0.8 oz. (23 g)	1.6 (46 g)

#### AWARNINGS:

- It is important that users of this tester read, understand, and follow all
  warnings, cautions, safety information, and instructions in the manual before
  operating or servicing this tester. Failure to follow instructions could result in
  death or serious injury.
- Risk of electric shock and burn. Contact with live circuits could result in death or serious injury.
- Use caution with voltages above 30V AC as a shock hazard may exist.
- A blinking or steady red glow and an audible beep indicate voltage present. If no indication, voltage could still be present.
- In bright light conditions, the LED visual indicators will be less visible.
- . Do not use if green LED is not illuminated.

#### AWARNINGS:

- Do not use if tester appears damaged or if the tester is not operating properly. If in doubt, replace the tester.
- Do not apply more than the rated voltage as marked on the tester (1000 volts AC).
- Always wear approved eye protection.
- Before each use, verify operation by testing a known working circuit that is within the rating of this tester.
- Do not rely on this tester with shielded wire. Operation may be affected by differences in socket design and insulation thickness and type.
- Comply with local and national safety requirements.
- If this tester is used in a manner not specified by the manufacturer, protection provided by the tester may be affected.

**ACAUTION:** Do not attempt to repair this tester. It contains no serviceable parts. Do not expose the product to extremes in temperature or high humidity.






# **Specialty Testers**

#### **12:1 Infrared Thermometer**

- Backlit display.
- Fahrenheit or Celsius.
- MAX. MIN. AVG. Differential calculations.
- 12:1 spot ratio allows quick checks of all types of environments, hazardous extreme temperature ranges, or remote areas.
- Temperature range of -58 to 1000°F (-50 to 538°C).



Distance to Object

7" (178 mm)

Width

3.25" (82.6 mm)



1.74" (44.2 mm)



Weight

8.1 oz. (230 g)



IR1000

# 12:1 Dual Laser Infrared Thermometer

Backlit display.

Cat. No.

IR1000

- Dual laser targeting.
- Fahrenheit or Celsius button.
- K-Type thermocouple input.
- 12:1 spot ratio.
- -76° to 1022°F measurement range.

**Batteries** 


2 x AAA


- Auto shut off.
- High/Low alarm.
- Auto-scan.
- Work light.

# Diameter at Spot **12"**(1 ft.) 24"(2 ft.) 48"(4 ft.)

Distance to Object

\*A NIST certified product is guaranteed to have been specially tested to ensure its accuracy. NIST certified meters are special order (lead time: 7 business days). NIST certifications are good for one year from the date of calibration.







IR2000



Cat. No. Batteries Width Height Depth Weight IR2000 2 x AAA 6.76" (171.7 mm) 1.87" (47.5 mm) 4.7" (119.4 mm) 9.0 oz. (255.1 g) IR2000N3 2 x AAA 6.76" (171.7 mm) 1.87" (47.5 mm) 4.7" (119.4 mm) 9.0 oz. (255.1 g)


# **Specialty Testers**

#### **30:1 Dual Laser Infrared Thermometer**

- Backlit display.
- Dual laser targeting.
- Fahrenheit or Celsius button.
- K-Type thermocouple input.
- 30:1 spot ratio.


- -76° to 1400°F measurement range.
- Auto shut off.
- High/Low alarm.
- Auto-scan.
- Work light.

#### Diameter at Spot



Distance to Object

\*A NIST certified product is guaranteed to have been specially tested to ensure its accuracy. NIST certified meters are special order (lead time: 7 business days). NIST certifications are good for one year from the date of calibration.





I	R	3	0	0	0

Cat. No.	Batteries	Height	Width	Depth	Weight
IR3000	2 x AAA	6.76" (171.7 mm)	1.87" (47.5 mm)	4.7" (119.4 mm)	9.0 oz. (255 g)
IR3000N*	2 x AAA	6.76" (171.7 mm)	1.87" (47.5 mm)	4.7" (119.4 mm)	9.0 oz. (255 g)

# **Digital Temperature Loggers**

#### **Dual Input Temperature Logger**

- IP67: Dust and waterproof.
- Differential temperature.
- Data logging.
- 9,999 memory positions.
- MIN, MAX, AVG & Hold.
- USB interface.
- Thermocouple temperature offset.
- Backlit display.
- Probe storage.

Thermocouple	Temperature Range °F	Temperature Range °C
J-Type	-346° to 2192°F	-210° to 1200°C
K-Type	-328° to 2498°F	-200° to 1370°C
T-Type	-328° to 752°F	-200° to 400°C
E-Type	-238° to 1832°F	-150° to 1000°C





DTL302

DTL304

Cat. No.	Inputs	Batteries	Height	Width	Depth	Weight	Included Accessories
DTL302	2	2 x AAA	7.20" (183 mm)	3.70" (94 mm)	1.70" (43 mm)	16.2 oz. (459 g)	magnetic hanger, thermocouples, usb power adapter & cable, software, batteries
DTL304	4	2 x AAA	7.20" (183 mm)	3.70" (94 mm)	1.70" (43 mm)	16.2 oz. (459 g)	magnetic hanger, thermocouples, usb power adapter & cable, software, batteries





# Video Borescope • Video/audio & photo recording. • Bright LED worklight. • IP67: Dust and waterproof camera. • Screen rotation. • TV-out & SD card. • File playback. Multiple Applications! • Electrical • HVAC • HVAC • Plumbing • Use to view inaccessible areas: • Inside a wall

Automotive

Aircraft

#### Package contents:

Main unit, gooseneck camera 17 mm, 18650 series 3.7v 2000mAh rechargeable Li-ion battery, mirror camera attachment, hook camera attachment, magnet camera attachment, USB power adapter/charger, USB data/charger cable, RCA composite A/V to 3.5 mm mini A/V cable, quick start guide, software/instruction manual CD-ROM, carrying case

ET500







- Down the drain

- In furnace or vent



Cat. No.	Batteries	Height	Width	Depth	Weight
ET500	2 x AAA	7" (178 mm)	3.25" (82.6 mm)	1.74" (44.2 mm)	8.1 oz. (230 g)

#### Borescope

- 2.4" color LCD.
- Bright LED work light.
- IP67: Dust and waterproof camera.
- Screen mirror.
- Auto power off.





#### Package contents:

Main unit, gooseneck camera 17 mm, mirror camera attachment, hook camera attachment, magnet camera attachment, USB power adapter/charger, USB data/charger cable.



- Electrical
- HVAC
- Plumbing
- Automotive
- Aircraft
- Use to view inaccessible areas:
  - Inside a wall
  - Down the drain
  - In furnace or vent

ET510 lithium ion 6.53" (165.9 mm) 2.84" (72.2 mm) 1.55" (39.4 mm) 8.08 oz. (229 g)	Cat. No.	Batteries	Height	Width	Depth	Weight
		lithium ion	h h'3" /1hh u mmi	2.84" (72.2 mm)	1.55" (39.4 mm)	8.08 oz. (229 g)

#### **Electrical Testers**

#### Receptacle Testers



Made in USA of US and imported parts.



- Designed to detect the most common wiring problems in standard receptacles.
- RT500

RT600

- Conditions indicated: wiring correct, open ground, reverse polarity, open hot, open neutral, hot/ground reversed.
- Conditions NOT indicated: quality of ground, multiple hot wires, combinations of defects, reversal of grounded and grounding conductors.

Cat. No.	GFCI	Dimensions	Weight
RT500	no	1.74" x 2.8" x 1.15" (44.2 mm x 71.1 mm x 29.2 mm)	1.95 oz. (55.3 g)
RT600	yes	1.74" x 2.8" x 1.15" (44.2 mm x 71.1 mm x 29.2 mm)	1.97 oz. (55.9 g)

#### Receptacle Testers



 Designed to detect the most common wiring problems in standard receptacles.

RT100

RT200

- Conditions indicated: wiring correct, open ground, reverse polarity, open hot, open neutral, hot/ground reversed.
- Conditions NOT indicated: quality of ground, multiple hot wires, combinations of defects, reversal of grounded and grounding conductors.

Cat. No.	GFCI	Dimensions	Weight
RT100	no	1.5" x 2.75" x 1" (38.1 mm x 69.9 mm x 25.4 mm)	1.27 oz. (36 g)
RT200	yes	1.5" x 2.75" x 1" (38.1 mm x 69.9 mm x 25.4 mm)	1.38 oz. (39.1 g)

#### **Continuity Tester**



- Tests for continuity of circuit with power off.
- Bulb in handle glows when circuit is complete (bulb included).
- Pointed 3-3/4" (95 mm) probe gets right to the problem.
- Deluxe 4" (102 mm) long handle with removable nylon cap holds replaceable bulb and battery.
- 36" (915 mm) test lead with alligator clip.
- Uses one AAA battery (not included).



Made in USA of US and imported parts.

Cat. No.	Overall Length	Weight (lbs.)
69133	probe to clip, 43-3/4" (1099 mm)	0.20 oz. (5.7 g)
Replacer	nent Part	
69131	replacement bulb for Cat. No. 69133	0.04 oz. (1.2 g)





- Device for checking live 6-24V, AC or DC circuits.
- 69127
- Tests for shorts in automotive and truck electrical systems, motor field coils, radio and low-voltage circuits, ground circuits of all lamps, wiring, fuses, etc.
- Bulb in handle glows when circuit is complete (bulb included).
- Pointed 3-3/4" (95 mm) probe makes checking easier.
- Deluxe 3-1/2" (89 mm) long handle with nylon top holds replaceable bulb.
- 36" (915 mm) test lead with alligator clip.



Made in USA of US and imported parts.

Cat. No.	Overall Length	Weight (lbs.)
69127	probe to clip, 43-1/4" (1099 mm)	0.20 oz. (5.7 g)
Replacem	nent Part	
69130	replacement bulb for Cat. No. 69127	0.01 oz. (.3 g)

#### **Circuit Tester**

- Tests circuits rated from 80 to 600 volts AC/DC.
- · High-visibility neon lamp indicator.
- High-impact, sealed 5-11/16" (144 mm) probe on long 24" (610 mm) leads for convenience in testing motors, fuses, relays, switches, etc.
- Resistor between each probe and lead.
- Reliable electronic components.

Cat. No.	Overall Length with Probes	Weight
69105	35" (889 mm)	2.4 oz. (68.1 g)



69105

#### **Electrical Testers**

#### **Multi-Volt Twin-Lead Tester**



69135

69128

- Tests for DC polarity, frequency, and polyphase line.
- Checks and indicates voltage on circuits up to 460 volts, AC or DC.
- Combination of glow lamps indicate voltage being tested—110, 220, 277, or 460 volts.
- Test leads furnished with probes on the ends.

Cat. No.	Overall Length	Weight
69135	7-7/8" (200 mm)	0.08 oz. (2.3 g)

#### **Low-Voltage Twin-Lead Tester**



- Tests 5-50 volt, AC or DC circuits and components.
- Built-in lamp glows if circuit is live.
- Each of the 4-1/2" (114 mm) test leads has an alligator clip on the end.
- Handy pocket clip.

Cat. No.	Overall Length	Weight
69134	8" (203 mm)	0.08 oz. (2.3 g)

#### **Test Lead Set**



- Red and black.
- Set of two 32" (813 mm) leads.
- Each lead has alligator clips attached to both ends.

Cat. No.	Overall Length	Weight
69128	32" (813 mm)	6.4 oz. (181.4 g)

#### Circuit Breaker Finder Accessory Kit



69411

- For use with ET300 Digital Circuit Breaker Finder.
- Light socket adapter for finding the correct circuit of a lighting fixture.
- Alligator clip adapter enables use of Digital Circuit Breaker Finder on bare wires.

Cat. No.	Description	Weight
69411	ET300 digital circuit breaker finder accessory kit	2.1 oz. (59.5 g)

#### **Replacement Test Lead Sets**

- Standard banana-type inputs compatible with most multimeters and clamp meters.
- Leads compatible with and fit lead storage compartments on most Klein meters.
- Leads also compatible with Klein MM100, MM200, CL100 and CL200 meters but not sized for lead storage compartments.
- Includes one pair each of universal test leads and alligator clips.
- Safety rating: CAT III 1000V / CAT IV 600V.

#### Additional Features for Premium Silicone Test Lead Set

- Silicone insulated for greater performance in temperature extremes.
- Enhanced strain relief and durability.



Cat. No.	Description	Overall Length	Weight
69410	universal test lead set	42" (1,067 mm)	3.2 oz. (90.7 g)
69416	universal premium silicone test lead set	48" (1,219 mm)	3.4 oz. (96.3 g)

# Electrical Te

## **Test & Measurement Line Accessories**

### **Replacement K-Type Thermocouples**








IR Gun	DTL	Weight
_	_	0.7 oz. (19.8 g)

**Clamp Meter** 

#### 6 mm Borescope Camera

Description



Bright LED worklight.

Cat. No

- IP67 gooseneck design for greater control and positioning.
- Smaller footprint when penetrating walls and panels.

Cat. No.	Dimensions	Weight
69450	6 mm x 1 m (0.24" x 3.3')	3.5 oz. (99.2 g)
69451	6 mm x 2 m (0.24" x 6.6')	5.5 oz. (155.9 g)

### 17 mm Borescope Camera



69413

- Bright LED worklight.
- IP67 gooseneck design for greater control and positioning.

Cat. No.	lo. Dimensions Weight	
69454	17 mm x 1 m (0.67" x 3.3')	9.5 oz. (269.3 g)

### 1 Meter Borescope Camera Extension



- Extends the reach of 17 mm borescope cameras.
- Up to two extensions may be used with 17 mm camera without loss of video quality (3 m / 9.9 ft.).
- Maximum of four extensions plus camera.
- Compatible with smaller diameter cameras.

Cat. No.	Dimensions	Weight
69455	17 mm x 1 m (0.67" x 3.3')	9.3 oz. (263.7 g)

### **Borescope Attachment Tools**



69457

Compatible with 17 mm diameter camera.

Cat. No.	Set Contains		Weight
69457			0.4 oz. (11.3 g)
	Descripton	Overall Length	
	mirror camera attachment	1.625" (44.3 mm)	
	hook camera attachment	3.00" (76.2 mm)	-
	magnet camera attachment	3.25" (82.6 mm)	-

## **Test & Measurement Line Accessories**

### **Line Splitter**

- Assists in measuring the current draw of a connected load up to 15A without splitting the load's power cord.
- Provides X10 mode and X1 mode.
- Designed for use with Klein Tools Test & Measurement Line (CL100, CL200, CL1000, CL1200, CL1300, CL2000, CL2200, CL2300, CL2500, CL3200).
- Works with many other manufacturers' clamp meters.

#### **AWARNINGS**:

- Do NOT use with loads greater than 15A.
  Risk of electric shock and burn. Contact with live circuits could result in death or serious injury.
  Do not use if line splitter appears damaged. If in doubt, replace line
- splitter. Do NOT use line splitter if wet. For indoors use only.

Cat. No.	Overall Length	Width	Weight
69400	6.2" (157 mm)	2.2" (558 mm)	3.9 oz. (110.6 g) w/ batteries





69400

### **Magnetic Hanger**

- For use with multimeters MM1000, MM1300, MM2000, MM2300, MM5000 and MM6000.
- · Clips securely into back of rubber boot.
- Strong magnet attaches securely to metal surfaces for hands-free use.

Cat. No.	Description	Weight
69190	magnetic hanger for electrician's multimeters	1.1 oz. (31.2 g)







## **Test & Measurement Line Accessories**

#### **Tradesman Pro™ Carrying Cases**











- Two layers of padding protect even delicate instruments.
- · Heavy-duty zipper and rugged PVC coated polyester for durability.
- One interior and one exterior pocket for quick access and organization.
- Sturdy handle with box stitching for secure transportation and convenient hanging.
- Constructed of 1680d ballistic weave.
- Cat. Nos. 69406 and 69407 recccomended for meters, testers, infrared guns and small tools.
- Cat. No. 69408 is recommended for meters, testers, borescopes, infrared guns and tools.

Cat. No.	Pockets	Width	Height	Depth	Weight
69406	1	4.50" (114 mm)	9.25" (235 mm)	2.25" (57 mm)	0.38 lbs. (0.17 kg)
69407	2	6.00" (152 mm)	10.25" (260 mm)	2.25" (57 mm)	0.53 lbs. (0.24 kg)
69408	2	7.00" (178 mm)	10.25" (260 mm)	2.25" (57 mm)	0.66 lbs. (0.30 kg)

### **Carrying Case**

- Constructed of 600 Denier nylon with a heavy-duty PVC zipper and zinc alloy zipper tag.
- Convenient storage for most Klein test and measurement products.



Cat. No.	Overall Size	Weight
69401	3-1/2" (89 mm) W x 9-1/2" (235 mm) H x 2 (50 mm)" D	2.5 oz. (70.9 g)









JOURNEYMAN







Cat. No.	Set Contains	Weight (lbs.)
80141		29.8

Cat. No.	Description
BLK12	12-piece ball-end hex-key caddy set – inch
J203-6	Journeyman™ standard long-nose pliers
J203-8N	Journeyman™ heavy-duty long-nose pliers – side-cutting & stripping
J502-10	10" Journeyman™ pump pliers with 1-3/4" (44 mm) jaw capacity
D507-8	8" adjustable wrench – extra capacity
D507-12	12" adjustable wrench – extra capacity
600-1	1/4" keystone-tip cushion-grip screwdriver – 1-1/2" (40 mm) round-shank
600-4	1/4" keystone-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty square-shank
601-3	3/16" cabinet-tip cushion-grip screwdriver – 3" (76 mm) round-shank
601-6	3/16" cabinet-tip cushion-grip screwdriver – 6" (152 mm) round-shank
602-6	5/16" keystone-tip cushion-grip screwdriver - 6" (152 mm) heavy-duty round-shank
603-1	No. 2 Phillips cushion-grip screwdriver – 1-1/2" (40 mm) round-shank
603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank

Cat. No.	Description
605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
7-piece cushion-grip nut driver set (3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")	
650	cushion-grip scratch awl
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv®
93125	25' x 1" tape measure with magnetic tip
931-9RE	torpedo level - magnetic
J1005	Journeyman™ crimping/cutting tool – non-insulated and insulated connectors
K1412	Klein-Kurve <sup>®</sup> dual NM cable stripper/cutter
J2000-9NETP	Journeyman™ high-leverage side-cutting pliers – fish tape pulling
J2000-48	Journeyman™ high-leverage diagonal-cutting pliers – angled head
5003-18	18" 10-pocket canvas tool bag with leather bottom
5139	canvas zipper bag
11055	Klein-Kurve $^{\circledR}$ wire stripper/cutter – 10-18 AWG solid & 12-20 AWG stranded
44133	Klein-Kurve® heavy-duty utility knife – quick change retractable blade
46037	cable-splicer's kit
56003	Steel Fish Tape - 125' L x 1/8" W
58889	padded adjustable shoulder strap
60053	standard protective eyewear
J63050	Journeyman™ high-leverage cable cutter
85191	conduit-fitting and reaming screwdriver

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  The tool belt provided in this kit is NOT an occupational protective belt.

 $\mbox{\bf \^AWARNING:}$  NOT insulated. Do NOT use these tools on or near live electrical circuits.

**AWARNING:** Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.



Cat. No.	Set Contains	Weight (lbs.)
80028		17.2

Cat. No.	Description
D203-8	heavy-duty long-nose pliers – side-cutting
D213-9NETP	high-leverage side-cutting pliers – fish tape pulling
D248-8	high-leverage diagonal-cutting pliers – angled head
D502-10	10" pump pliers with 1-3/4" (44 mm) jaw capacity
506-10	10" adjustable wrench – standard capacity
600-4	1/4" keystone-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty square-shank
601-6	3/16" cabinet-tip cushion-grip screwdriver – 6" (152 mm) round-shank
602-6	5/16" keystone-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank
605-6	1/4" cabinet-tip screwdriver – 6" (152 mm) heavy-duty round-shank
631	7-piece cushion-grip nut driver set (3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv <sup>®</sup>

Cat. No.	Description				
93025	25' x 1" tape measure				
930-9	magnetic torpedo level				
1005	crimping/cutting tool – non-insulated and insulated connectors				
5102-16	16" canvas tool bag				
5139	canvas zipper bag				
11045	wire stripper/cutter – 10-18 AWG solid wire				
44100	utility knife – retractable blade				
60056	frameless protective eyewear				
85191	conduit-fitting and reaming screwdriver				

80028

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  The tool belt provided in this kit is NOT an occupational protective belt.

**AWARNING:** NOT insulated. Do NOT use these tools on or near live electrical circuits.

**AWARNING:** Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.





JOURNEYMAN



Cat. No.	Set Contains	١	Weight (lbs.)
80118		1	1.6

Cat. No.	Description
J203-8N	Journeyman™ heavy-duty long-nose pliers – side-cutting & stripping
J502-10	10" Journeyman™ pump pliers with 1-3/4" (44 mm) jaw capacity
D507-10	10" adjustable wrench – extra capacity
603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank
605-4	1/4" cabinet-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty round-shank
605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
630-1/4	1/4" cushion-grip nut driver – 3" (76 mm) shank
630-5/16	5/16" cushion-grip nut driver – 3" (76 mm) shank
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank

Cat. No.	Description
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv®
93125	25' x 1" tape measure with magnetic tip
J2000- 9NETP	Journeyman™ high-leverage side-cutting pliers – fish tape pulling
J2000-48	Journeyman™ high-leverage diagonal-cutting pliers - angled head
5165	10-pocket leather tool pouch
5705	Powerline™ web work belt
11055	Klein-Kurve <sup>®</sup> wire stripper/cutter – 10-18 AWG solid & 12-20 AWG stranded
60053	standard protective eyewear

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\pmb{\triangle} \textbf{WARNING:}$  The tool belt provided in this kit is NOT an occupational protective belt.

**AWARNING:** NOT insulated. Do NOT use these tools on or near live electrical circuits.

**AWARNING:** Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.

## **Tool Sets**

### **14-Piece Electrician Tool Set**

l	Cat. No.	Set Contai	ns	Weight (lbs.)
	80014			9.6
		Cat. No.	Description	
		D203-8	heavy-duty long-nose pliers – side-cutting	(11)
		D213- 9NETP	high-leverage side-cutting pliers – fish tape pulling	1
		D248-8	high-leverage diagonal-cutting pliers – angled head	9
		D502-10	10" pump pliers with 1-3/4" (44 mm) jaw capacity	
		603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank	1
		603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank	
		605-4	1/4" cabinet-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty round-shank	
		605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank	25
		670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv <sup>®</sup>	4
		93025	25' x 1" tape measure	- 7
		5164	8-pocket leather tool pouch	
		5225	adjustable web tool belt	
		11045	wire stripper/cutter – 10-18 AWG solid wire	
		60056	frameless protective eyewear	



#### **12-Piece Electrician Tool Set**

Cat. No.	Set Contain	S	Weight (lbs.)
5300			6.82
	Cat. No.	Description	
	5166	7-pocket leather tool pouch	_
	5225	adjustable web belt	_
	603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank	
	603-4	No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank	_
	605-4	1/4" cabinet-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty round-shank	
	605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank	
	11045	wire stripper/cutter – 10-18 AWG solid wire	_
	D248-8	high-leverage diagonal-cutting pliers – angled head	_
	D203-8	heavy-duty long-nose pliers – side-cutting	_
	D213-9NETP	high-leverage side-cutting pliers – fish tape pulling	_
	D502-10	pump pliers with 1-3/4" (44 mm) jaw capacity	_
	928-25HV	high-visibility power-return measuring tape	_



5300

All dimensions are in inches and (millimeters) unless otherwise specified.

 $\ensuremath{ \widehat{\textbf{AWARNING:}}}$  The tool belt provided in this kit is NOT an occupational protective belt.

**AWARNING:** Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.





### **12-Piece Electrician Tool Set**



Cat. No.	Set Contains		Weight (lb
92003			17
	Cat. No.	Description	
	D213-9NETP	9" high-leverage side-cutting pliers – fish tape pulling	-
	D248-8	8" high-leverage diagonal-cutting pliers	
	D203-8	8" heavy duty long-nose pliers – side-cutting	
	D502-10	10" pump pliers	_
	11045	wire stripper/cutter	_
	93275	metric/english tape measure with magnetic tip	_
	603-4	No. 2 profilated Phillips tip scewdriver – 4" round shank	
	605-4	1/4" cabinet tip cushion-grip screwdriver – 4" heavy duty round shank	_
	661	No.1 square-recess tip screwdriver – 4" round shank	_
	662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank	
	5719	18 Pocket Tool Pouch	

All dimensions are in inches and (millimeters) unless otherwise specified.

5705

 $\pmb{\triangle} \textbf{WARNING:}$  The tool belt provided in this kit is NOT an occupational protective belt.

**AWARNING:** NOT insulated. Do NOT use these tools on or near live electrical circuits.

Powerline™ web work belt

**AWARNING:** Do NOT use screwdrivers to pry or chisel.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.

# Index – Alphabetica

# **Alphabetical Index**

Item Page	Item Page	Item Pag
10-in-1 Folding Screwdriver/Nut Driver	Cable Cutter, Armored	F
10-in-1 Screwdriver/Nut Driver	Cable Cutters. 63-68	F to BNC Adapter
11-in-1 Schrader® Valve Removal/Installation Bit 97	Cable Cutters, Insulated	F to RCA Adapter
1-in-1 Screwdriver/Nut Driver. 97	Canvas Tool Bags	F-Splice Adapter 3 GHz
18° High-Speed Drill Bits	Carbide Hole Cutter284	Fasteners, Sheet Metal
2-Piece Electrician Tool Set	Carbide-Tipped Hole Cutter Kits	Fiberglass Tape Measure
4-Piece Electrician Tool Set	Carbide-Tipped, Masonry Drill Bits289	Fish Tape Accessories
8-Piece Journeyman™ Tool Set330	Chisels	Fish Tape Pulling Pliers
2000 Series <sup>®</sup> Pliers .8, 12, 25-27, 64, 72, 73, 76, 77, 162	Clamp Meters	Fish Tapes
8-Piece Electrician Tool Set	Cleaners	Fish Tapes, Nylon
3-in-1 Impact Socket Wrench	Coaxial Tools	Fish Tapes, Steel
I-in-1 Screwdriver	Combination Tool Apron	Flex-Bit Extensions
I-in-1 Tube Bender	Combination Tools	Flex-Bit Kit280
I-Piece Carbide Hole Cutter Kit	Combination Wrenches	Flex-Bit Placement Tool
I1-Piece Journeyman™ Tool Set	Compression Connectors, Universal 43	Flexible Drill Bits
5-in-1 Screwdriver/Nut Driver	Compression Connectors, Universal BNC 43	Folding Hex-Keys
3-Piece Master Electrician's Hole Cutter Kit284	Compression Connectors, Universal F	Full Face Shield
90° F-Adapter 3 GHz	Compression Connectors, Universal RCA	G
4	Conduit Bender Handles	Gloves
Adapter, 90° F	Conduit Benders	Gloves, Journeyman™
Adapter, F to BNC	Conduit Pliers	Grips, Copper/Steel Strand – Chicago®
Adapter, F to RCA	Conduit Scoring Tool	Grips, Interchangeable
Adapter, F-Splice 44	Conduit Tools	Grips, Steel Strand – Chicago <sup>®</sup>
Adjustable Hole Saw	Connecting Bars	Grips, Steel Strand – Haven's®
Adjustable Wrenches 124, 125	Construction Bars	Grips, Wire Pulling Accessories
Aerial Aprons	Construction Tools	Grizzly® Bar
Anchors	Construction Wrenches	Guards, Tool 190
Apron, Combination Tool	Copper/Steel Strand – Chicago® Grips	H
Apron, Electrician's Tool	Crimping Tools 60, 61, 275	Hacksaw, Dual-Purpose
Aprons, Aerial	Crimping/Cutting Insulated	Hacksaws
Armored Cable Cutter	Cushion Grip Nut Driver Sets 107-109	Hammers 266, 267, 277, 304-306
ASCR (Aluminum Conductor Steel Reinforced) . 232-235	Cushion Grip Nut Drivers	Handles, Conduit Bender
Aviation Snips	Cushion Grip Screwdriver Set. 87-90	Hard Hats, Caps and Accessories
Avis	1	
awis	Cutters, Bolt 68, 69	Heavy Duty Tie Wire Belts, Ironworker's
Bag's, Electrician's	Cutters, Cable 63-68 Cutters, PVC	Hex-Key Sets 139-147
Bags, Storage 200-213	,	Hex-Key Wrenches 139
Bags, Tool. 200-211	Cutters, Tube	Hex-Keys, Folding
Bar, Grizzly <sup>®</sup>	Cutters, Wire	Hex-Keys, L-Style. 145-147
	Cutting & Notching Tools 270-274	Hex-Keys, T-Handle
Bars, Connecting		Hole Saw Kit, Electrician's
Bars, Construction	Diagonal Cutting Pliers	Hole Saw Kit, Journeyman™
Bars, Mining	Disposable Dust Mask	Hole Saw Kits
Belts, Tool. 196, 197	Drill Bit Sets	Hole Saws
Sender, Tube 4-in-1	Drill Bits, Flexible	Hole-Saw Arbors and Accessories
Benders, Conduit	Drivers, Magnetic Hex	Hooks, Lineman
Benders, Tube	Dual-Purpose Hacksaw	
Bent, Trimmers	Duct Stretching & Slitting Tools	Industrial High-Leverage Shears
Bit Set, Magnetic Screwdriver	E	Industrial Utility Snips
Sits, Carbide-Tipped Masonry	Electrical Test & Measurement	Insulated Cable Cutters
3its, Drill	Electrical Testers	Insulated Crimping/Cutting
Bits, Replacement	Electrician's Bags	Insulated Diagonal Cutting Pliers
Bits, Ship-Auger287	Electrician's Insulated Cable Cutters	Insulated Lineman's Skinning Knife
Bits, Step-Drill286	Electrician's Insulated Pliers	Insulated Long-Nose Pliers
Block and Tackle	Electrician's Tool Apron	Insulated Nut Drivers
Bolt Cutters	Electrician's Tool Belt, Tradesman Pro™	Insulated Pliers
C	Electrician's Hole Saw Kit	Insulated Pump Pliers74
Cable Benders	Electrician's Scissors	Insulated Screwdrivers



Alphabetical Index

334

#### Item Page Page Item Page Item Pliers, Journeyman™, Diagonal Cutting . . . . . . 27 Meters, Clamp 313-315 Pliers, Journeyman™, Long Nose . . . . . . . . . 27-28 Insulated Tool Kits 81-84 Pliers, Lightweight Flush Cutter ..... 15 Mining & Heavy Industry Tools 259-268 Pliers, Lineman's 9 Interchangeable Jaw Grips & Liners .......247 Mining Bars ......262 96, 97, Multi-Bit Nut Drivers Pliers, Pump 22 Multi-Bit Screwdriver Replacement Parts . . . . . . . . . . . 98 Pliers. Side-Cutting 8-11 Pliers, Slip Joint. 21 Journeyman™ Gloves . . . . . . . . . . . . . . . . . . 172-175 Power Conduit Reamer 94 Journeyman™ Snips......270 Nut Drivers, Insulated 80 Journeyman™ Crimping Pliers . . . . . . . . . . . . 28 Nut Drivers, Multi-Bit 96, 97 Journeyman™ Diagonal Cutting Pliers . . . . . . . . . 27 Journeyman™ Long Nose Pliers . . . . . . . . . . 27-28 Offset Snips 270-271 Protective Equipment, Personal .............................. 167-178 Padded Suspenders, Tradesman Pro™......191 Personal Protective Equipment . . . . . . . . . . . . 167-178 LAN Scout<sup>TM</sup> Jr. Tester 145-147 Pliers . . . . . . . . . . . . 8-22, 72-74, 76-78 Replacement Parts. Multi-Bit Screwdriver/Nut Drivers 98 Lineman Buckets . . . . . . . . . . . . . . . . . . 215-219 Pliers, 2000 Series<sup>®</sup> .8, 12, 25-27, 64, 72, 73, 76, 77, 162 Pliers, Combination 10 Pliers, Diagonal-Cutting. 11-14 Lineman's Skinning Knife, Insulated . . . . . . . . . . . . 80 Pliers, Handles 23 Schrader® Valve Removal/Installation Bit 11-in-1.... 97 Pliers, Insulated Diagonal Cutting ......72. 73 Screwdriver, 10-in-1......97 Magnetic Screwdriver Bit Set . . . . . . . . . . . . 99

Pliers, Journeyman™, Crimping . . . . . . . . . . . 28

Screwdriver, 4-in-1

# Index — Alphabetica

# **Alphabetical Index**

Item	Page	Item	Page	Item Page
Screwdriver, 5-in-1.	97	Tapes, Warning	178	Tube Flaring & Swaging Tools
Screwdriver, Conduit-Fitting and Reaming	94	Tapping Tools		Types of Jaw Contours
Screwdriver/Nut Driver Folding 10-in-1	97	Telecom Tools	30-32	Types of Wire Pulling Grips230
Screwdrivers	80 86-106	Test & Measurement Line Accessories.	324-326	Tyre Products268
Screwdrivers Plastic Handle Sets	102	Testers, Electrical	317-319	U
Screwdrivers, Cushion Grip	87-93	Testers, Electrical	322-324	Universal Compression Connectors
Screwdrivers, Cushion Grip	87-93	Testers, Non-Contact Voltage	318	Universal Compression Connectors, BNC 43
Screwdrivers, Insulated	79, 80	Testers, Specialty	319-321	Universal Compression Connectors, F 43
Screwdrivers, Journeyman™	. 100, 101	Tire Wire Reel	256	Universal Compression Connectors, RCA 43
Screwdrivers, Multi-Bit	96, 97	Tool Bag, Accessories	211	Universal Side-Cutting Pliers
Screwdrivers, Multi-Bit	96, 97	Tool Bags		Utility Knife, Auto Loading Retractable
Screwdrivers, Offset	106	Tool Bags, Canvas	205, 206	Utility Knife, Folding300
Screwdrivers, Plastic Handle, Specialty	. 104, 105	Tool Bags, Leather		Utility Knife, Folding Retractable
Screwdrivers, Specialty		Tool Bags, Totes		Utility Knife, Klein Kurve® Retractable
Seaming & Folding Tools		Tool Bags, Tradesman Pro™®		Utility Knives
Sets, Tool	,	Tool Bags, Vinyl		Utility Knives and Blades
Sharpening Tools		Tool Belts		V
Shears, Industrial High-Leverage		Tool Belts and Pouch Sets		Video Borescope
Sheet Metal Fasteners		Tool Boxes, Metal.		Vinyl Tool Bags
Sheet Metal Tools/HVAC		Tool Combination Apron		Voice/Data/Video Connectors
Ship-Auger Bits		Tool Guards		Voice/Data/Video Tester Kits. 48, 49, 50, 51, 54
Side-Cutting Pliers		Tool Holders		Voice/Data/Video Testers
Slide Racks		Tool Kits, Insulated		Voice/Data/Video Tool Kits
Slings, Lineman	,	Tool Pouches		Voice/Data/Video Tools 34-42
Snips.		Tool Pouches, Powerline™ Series		W
Snips, Aviation	,			Warning Tapes
•		Tool Set, 12-Piece Electrician		Web Work Belt, Powerline™ Series
Snips, Industrial Utility		Tool Set, 14-Piece Electrician		Wide Range of Cables 245-246
Snips, Journeyman™		Tool Set, 18-Piece Journeyman™		Wire Cutters
Snips, Offset		Tool Set, 28-Piece Electrician		Wire Mesh Grips
Snips, Right Angle		Tool Set, 41-Piece Journeyman™		Wire Pulling Grips 243-254
Socket Wrench Sets	/	Tool Sets		Wire Pulling Grips Accessories
Socket Wrenches	- ,	Tools, Awls		Wire Pulling Lubricant
Special-Purpose Knives.		Tools, Combination.		·
Specialty Clamp Meters.		Tools, Conduit		Wire Pulling Supplies
Specialty Plastic Handle Screwdrivers		Tools, Conduit Scoring		Wire Stripper/Cutter, Katapult. 58
Specialty Screwdrivers		Tools, Construction		Wire Strippers
Specialty Screwdrivers		Tools, Crimping		Wrench Sets 126-134
Specialty Screwdrivers		Tools, Cutting & Notching		Wrench Sets, Ratcheting Box
Specialty Testers		Tools, Cutting & Notching		Wrenches
Specialty Wrenches		Tools, Duct Stretching.		Wrenches, 3-in-1 Impact Socket
Spring Tool Set		Tools, Duct Stretching & Slitting		Wrenches, Adjustable
Spring Tools		Tools, Nylon Tie Tensioning		Wrenches, Combination
Steel Construction Tools		Tools, Seaming & Folding		Wrenches, Construction
Steel Fish Tapes		Tools, Sharpening		Wrenches, Hex-Key
Steel Strand – Chicago® Grips		Tools, Slitting		Wrenches, Open-End
Steel Strand – Haven's®w Grips	244	Tools, Spring		Wrenches, Ratcheting Box Sets
Step-Drill Bits		Tools, Steel Construction		Wrenches, Ratcheting Offset Box
Storage Bags		Tools, Tapping		Wrenches, Refrigeration276
Strap Wrenches		Tools, Tube Flaring & Swaging	274	Wrenches, Socket
Stripper/Cutters, Insulated	75, 78	Torque Wrenches		Wrenches, Socket Sets
Strippers, Insulated	75, 78	Tradesman Pro™		Wrenches, Specialty
Strippers, Wire56,	57, 58, 59	Tradesman Pro™ Organizer - Electrician'		Wrenches, Strap138
Swaging Tool – Punch Type	274	Tradesman Pro™ Organizer Bags	201-204	Wrenches, Torque
T		Tradesman Pro™ Padded Suspenders .	191	
T-Handle Hex-Keys	. 140-143	Tube Benders	273	

Tube Cutter Accessories .......274

Tube Cutters .......274



					Page
A 000	103	1001	59	1106	189
VDV 001-081	39	KSCK-100-1	254	11061	59
VDV 002-818	47	KSSK-100-1	254	11063W	58
VDV 002-820	47	KPS-100-2	254	11073	58
JSDS 01	100	KP- 100-24	253	11081	58
V01	105	1003	58	11082	58
A 010	102	KPS- 100-3	254	BD 111	103
VDV 012-811	46	<b>KP-</b> 100-36	253	VDV 113-021	35
JSDS 02	101	1004	58	<b>VDV</b> 113-022	35
V 02	105	1005	60	<b>VDV</b> 113-802	35
VDV 026-049	30	1005-INS	74	<b>VDV</b> 113-804	35
VDV 026-049	31	J 1005	28	PH 1-1-5	120
VDV 026-049	38	J 1005	60	<b>SQ</b> 1-1-5	120
VDV 026-812	46	1006	60	<b>\$</b> 116	114
VDV 027-813	46	<b>VDV</b> 100-801	35	A 116-2	102
V 03	105	1010	59	A 116-3	102
V 04	105	1011	58	A 116-4	102
V 05	105	1016	60	BL 12	
KPM- 050	253	<b>\$</b> 1018	114	BLK 12	145
KPS 050	280	\$1018M	114	LL 12.	147
KPS- 050-2	254	\$1018M		LLK12	146
DK 06.		<b>\$</b> 106		P12	
KPS- 062-2		\$106M		<b>\$</b> 12	
KPM- 075		\$11		\$12H	
KPS 075		1100L		SS 12	
KSSK-075-1		J1100L		P120	
KPS- 075-2		VDV 110-003.		1200BI	
KP- 075-24		VDV 110-004		1200BI-P	
KP- 075-36		VDV 110-020.		CL 1200	
NCVT-1		VDV 110-046.		VDV 120-005.	
10		VDV 110-061	• • • • • • • • • • • • • • • • • • • •	VDV 120-006	
BL 10.		VDV 110-095.		12098	
BLM 10		1101R		12098-EINS	
BLMK10		J1101R		12098-INS	
LLM 10		11028		J12098	
LMK10		J1102S		PND 1210.	
\$10	•	1104.		1218BI	
\$10M		11045		1218BI-P	
SS 10.		11045-INS	•	BD 122	
CL 100		11046		1224BI	
ET 100		11047	•	1224BI-P	
KPJ- 100		11048		1232Bl	
KPM-100		11049		1232BI-P	
MM 100		11049-INS		PND 125	
RT 100		11053		KPL-125-1	
1000		11054		KSSK-125-1	
CL 1000		11054-EINS		KPS-125-2	
IR 1000		11055		\$126	
MM 1000	312	11055-INS	75	<b>\$</b> 126M	114



# Index — Numerica

Item	Page	Item	Page	Item	Page
MM 1300	312	BL 16	146	1628-30R	241
MM 1300N	312	K 16	105	1628-30\$	235
A 130-2	102	LL 16	147	1628-308	241
A 130-3	102	<b>§</b> 16	114	1628-30T	235
A 131-2	102	1604-10	244	1628-30T	241
BD 133	103	1604-20.	244	1628-30U	235
PH 1-35-5	120	1611-20	242	1628-30U	241
<b>SQ</b> 1-35-5	120	1611-30	242	1628-40A	235
BL 14	146	1611-40	242	1628-40A	241
K 14	105	1611-50	242	1628-40U	235
LL 14	147	1613-30	244	1628-40U	241
<b>S</b> 14	114	1613-40	243	1628-40VRU	235
K 1412	56	PH 1-6-2	120	1628-40W	235
K 1412CAN	56	<b>SQ</b> 1-6-2	120	1628-40W	241
<b>SL</b> 14-1-5	120	1625-20	230	1628-40X	235
BD 143	103	1625-20	244	1628-40X	241
<b>SL</b> 14-35-5	120	1625-20 1	244	1628-40Y	235
BD 144	103	1625-20 7/8	244	1628-40Y	241
BD 146	103	1628-16		1628-40Z	
<b>\$</b> 146	114	1628-16AT	32	1628-40Z	241
BLM 15	146	1628-16AT	243	1628-50	
LLM 15	147	1628-16P		1628-50A	241
KN 1500P-EX	226	1628-16PE		1628-50B	241
KPL- 150-1	253	1628-16PE	239	1628-50D	241
KPS- 150-2		1628-16PF	233	1628-50E	241
KPS- 150-3	254	1628-16PF.		1628-50P	
KP- 150-36	253	1628-16PG	233		241
KT 151T	136	1628-16PG	239	1628-50S	241
1515-S	301	1628-16PH	233	1628-50T	
1515-1		1628-16PH	239	1628-50U	
KT 155HD	136	1628-16PI	233	1628-50W	241
KT 155T		1628-16PJ		1628-50X	
1550-10		1628-16PJ			241
1550-11		1628-16PK			241
1550-14	297	1628-16PK			247
1550-2		1628-16PL			247
1550-24	297	1628-16PL	239		233
1550-4		1628-16PM	233	1656-20	239
1550-42	298	1628-16PM			242
1550-44	297	1628-16PN		1656-30	
1550-45.		1628-16PN		1656-30	
1550-5		1628-17		1656-30	
1550-6		1628-18.			242
1550-7		1628-30		1656-40	
1550-9		1628-30N		1656-40	
BD 156		1628-30N			242
1560-3		1628-300			233
1570-3		1628-300		1656-50.	
1570-3LR		1628-30P			242
1571-INS		1628-30R			242
101 I-IIIO	00	1020 <b>-</b> 30N	230	1000-00	

m	Page	Item	Page	Item	Page
1656-60	239	BL 2	146	<b>VDV</b> 201-040	42
1656-60	242	BLM 2	146	VDV 201-042	42
1659-20	242	LL 2	147	2012	220
1659-30	242	LLM 2	147	201-7CST	11
1659-40	242	NCVT-2	318	D 201-7CST	11
1659-5AT	32	NHRDA 2	136	D 201-7NE	10
1659-5AT	243	NRHD 2	136	D 201-8	10
1659-50	242	BL 20	146	D 201-8NE	10
1671-10	246	LL 20	147	D 201-9	10
1672-10	246	<b>\$</b> 20	114	D 201-9NE	10
1684-5	243	CL 200	315	D 202-6	13
1684-5AT	32	ET 200	317	D 202-6C	13
1684-5AT	243	MM 200	312	203-6-EINS	78
1684-5F	243	RT 200	322	D 203-6	17
1684-74	243	CL 2000	315	D 203-6-INS	74
1685-20	246	IR 2000	319	D 203-6C	17
1685-31	246	IR 2000N	319	D 203-6SCPC	19
1686-10	246	MM 2000	312	J 203-6	28
1686-20	246	MM 2000N	312	D 203-6H2	31
1692-5	243	2000-28-EINS	77	203-7-EINS	78
1692-5AT	32	D 2000-28		D 203-7	17
1692-5AT	243	D 2000-28-INS	72	D 203-7-INS	74
1692-5AT	243	J 2000-28.	27	D 203-7C	
1702-20N	226	2000-48-EINS	77	J 203-7	
T1710	61	D 2000-48.	12	203-8-EINS	
T1715	61	D 2000-48-INS	73	D 203-8-INS	
P 18.		J 2000-48.		D 203-8N	
\$ 18.		D 2000-7		D 203-8N-INS	
\$ 18H		D 2000-7CST		D 203-8NCR	
1802-30		D 2000-8		J 203-8.	
1802-30S	224	J 2000-8	26	J 203-8N	97
H 1802-30	225	2000-9NE-EINS		VDV 205-035	42
H 1802-30 S		D 2000-9NE		VDV 205-036	
1802-30 S/R		D 2000-9NE-INS	•	VDV 205-039	
1802-30S S/R		D 2000-9NECR		VDV 205-044	
H 1802-30 S/R		D 2000-9NETH	9	D 206-8C	
H 1802-30S S/R		D 2000-9NETP		J2068C	
1803-60		D 2000-9ST		D 209-4C	
1804-60		HD 2000-9NE		K21	
K19		J 2000-9NE	•	2100L	
19351		J 2000-9NECR		J2100L	
19352		J 2000-9NECRTP		2100-5	
19353		J 2000-9NECRTP		2100-7	
19353		J 2000-9NETP		2100-8	
19353		J 2000-9NETP		2100-9	
19353		KPL- 200-1		2101R	
19542		J 2001-7NE		J2101R	
19543		KPS- 200-2		210122	
19544		KPS- 200-3.		2102S	
19555		2006.		J2102S	
1 3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0		LUUU	UI	U C 1 U C U	



# Index — Numerica

Item	Page	Item	Page	Item	Page
2103	271	D 220-7	13	D 252-6SW	13
J2103S	270	D 220-7-INS	73	25450	248
J 2104L	270	KT 223X4	137	D 257-4	14
J 2105R	270	KT 223X4-INS	137	D 257-4C	14
D 210-6C	14	VDV 226-011	38	258	223
J2106S	271	VDV 226-011	38	259	223
VDV 211-037	42	VDV 226-817	47	D 259-4C	15
VDV 211-038	42	D 227-7C	21	PH 2-6-2	120
VDV 211-041		D 228-7		<b>SQ</b> 2-6-2	
VDV 211-043	42	D 228-8	12	267	223
VDV 211-048	37	D 228-8-INS	72	H 267	223
VDV 211-063	37	J 228-8	27	268	223
PH 2-1-15		D 2291		H 268	223
<b>SQ</b> 2115.	94	D 2291	31	27400	
<b>SQ</b> 2-1-15	120	K 23.	105	27450	
VDV 212-008.		CL 2300		D 275-5	
VDV 212-034		MM 2300.		K 28.	
213-8NE-EINS		MM 2300N		BD 284	
D 213-8NE		23008		BD 286	
D 213-8NE		23010		D 295-4C	
J 213-8NE		23011		BLM 3	
213-9NE		23015		LLM 3	
213-9NE-EINS		D 230-4C		CL 3000.	
213-9ST		D 232-8		IR 3000	
D 213-9.		SK 234		IR 3000N	
D 213-9NE		D 234-6		KPS- 300-2	
D 213-9NE		D 234-6.		D 301-5C	
D 213-9NE-INS		D 234-6C	•	D 301-6.	
D 213-9NECR		PH 2-35-5	•	D 301-6.	
D 213-9NECR-INS		<b>SQ</b> 2-35-5		D 301-6C	
D 213-9NETH		D 238-8		D 301-7C	
D 213-9NETP		BL 24		DTL 302	
D 213-9ST		LL 24		D 302-6.	
HD 213-9NE	•	24000		DTL 304	
HD 213-9NETH		24001		BD 306	
J 213-9NE	•	24005		D 307-5 1/2C	
J 213-9NECR		D 240-6.		BD 308	
J 213-9NETP		D 243-8		3100.	
J 213-9NETP		D 244-5C		CL 3100	
A 216-10		D 245-5		3101	
A 216-2		D 245-5		D 310-6C	
A 216-3.		D 245-5C		31084	
A 216-4.		D 248-8-INS		VDV 312-012	
A 216-6		J 248-8		3146B	
A 216-8		D 248-9ST		3146B	
CL 2200		BLM 25		PH 3-1-5	
22000		LLM 25		<b>SQ</b> 3-1-5	
22001		CL 2500		31510	
22002		KPS- 250-2		31512	
22003	302	D 252-6	13	31514	282



/4	LE	IN	
	OP. We be		1
EST,		)189	57
\s	`\. \\.	1.6,	
	ٽ		

	Ц
КИ	ı
U II	ŭ

Item	Page	Item	Page	Item	Page
31516	282	31734	294	3212	258
31518	282	31734-15	294	3213	137
31520	282	31738	294	3213	258
31522	282	31738-15	294	3214	137
31524	282	31742	294	3214	258
31526	282	31742-15	294	D 321-4 1/2C	18
31528	282	31746	294	3219	137
31532	282	31746-15	294	3219	258
31534	282	D 317-5C	19	3220	137
31536	282	31750	294	3220	258
31538	282	31750-15	294	3221	137
31540	282	31754	294	3221	258
31542	282	31756	294	32215	95
31544	282	31758	294	32216	95
31548	282	31758-15	294	3222	137
31552	282	31762	294	3222	258
31556	282	31764	294	3223	137
31558	282	31766	294	3223	258
31558	282	31802	294	3224	137
31564	282	31806	294	3224	258
31566	282	31808	294	D 322-4 1/2C	18
31572	282	31810	294	3227	125
31576	282	31832	294	3227	137
31580	282	31834		3227	258
31596		31836		3231	
31600SEN	282	31838		3231	258
31606		31840		3232	
SL 316-1-5		D 318-5 1/2C		D 323-4 1/2C	
31630		31850		3238.	
31635		31852		3238	
SL 316-35-5		31854		3239.	
31640		31856		3239	
31645		31857		3239	
31650		31858		32392	
31655		31860		32394	
31660		31862		32395	
31665		31864		32396	
31670		31866		32397	
31710		31868		32398	
31710-15		31870		32399	
31714		31872		3240	
31716		31873		32400	
31716-15		CL 3200		32401	
31720		CL 3200N		3241	
31722		D 320-4 1/2C		32410	
31722-15		3210		32411	
31722-50		3210		32412	
31728		3211		3242	
31728-15		3211		3243	
31728-50	294	3212	137	3244	257

# **Index — Numerica**

Item	Page	Item	Page	Item	Page
3245	257	32560	96	40012	176
3246	257	32561	96	40014	176
32460	104	32562	96	40015	176
3247	257	3257	257	40016	176
32473	104	3258	257	40017	176
32476	97	3259	257	40018	176
32477	97	3260	257	40020	176
	98	32605	119		176
	104	32606			176
	98	3261			174
	104	3262			174
	257	3263			174
	98	3265			174
	98	VDV 327-103			174
	98	D 327-5 1/2C			174
	98	32759			174
	96	D 328-5 1/2C			174
					174
	257	D 333-8			
	99	33525			174
	257	33525SC			174
	99	33526			174
	99	33527			175
	97	33528			175
	276	33529			175
	97	33532-INS			175
32535	97	PH 3-35-5		40058	175
32536	97	<b>SQ</b> 3-35-5	120	40059	175
32537	97	D 335-5 1/2C	19	40062	175
32538	97	K 34	105	40063	175
32539	97	P 340	105	40064	175
32540	98	3416	136	40067	175
32541	98	3416A	136	40068	175
32542	98	KPS-350-2	254	40069	175
32543	98	K 36	105	40072	177
32544	98	PH 3-6-2	120	40074	177
32545	98	<b>SQ</b> 3-6-2	120	40080	177
32546	98	D 366-6C	20	40082	177
32547	98	K 38	105	40084	177
32548	98	BL 4	146	40086	177
32549	98	BLM 4	146	40205	172
3255	257	LL 4	147	40206	172
32550	98	LLM 4	147	40207	172
32551	98	ST 4	116	40208	172
32552	98	40001	177	40209	172
	98	40002			172
	98	40003			172
	96	40004			172
	96	40006			172
	96	40008			173
	257	40010			173
J2JU	201	40010	1/0	40210	113

Item	Page	Item	Page	Item	Page
40216	173	42245	185	KT 4501	245
40217	173	42246	185	KT 4502	245
40218	173	42247	183	45200	178
40219	173	4BP25	262	45201	178
40220	173	4HT25	104	455	223
40221	173	4HT27	104	K 46	105
40222	173	VDV 427-015	41	KT 4600	245
JSD 4C06	101	VDV 427-016	41	KT 4601	245
JTH 4E06	140	VDV 427-017	41	KT 4602	245
JTH 4E06	141	VDV 427-018	41	46037	301
JTH 4E07	140	VDV 427-104	41	46039	301
JTH 4E07	141	VDV 427-800	40	KT 4650	245
JSD 4K08	101	VDV 427-805	40	KT 4652	245
JTH 4E08	140	VDV 427-806	40	470	226
JTH 4E08	141	VDV 427-807	39	K 48	105
JTH 4E09	140	VDV 427-807	40	KT 4800	245
JTH 4E09	141	VDV 427-822	39	KT 4801	
JSD 4PH1	101	4HS316	104	KT 4802	245
4BP10	262	K 44	105	48036	299
JTH 4E10	140	44000	296	48502	223
JTH 4E10	141	44000-BLK	296	<b>ST</b> 49	116
JTH 410E	140	44001	296	4HS932	104
JTH 410E	141	44001-BLK	296	5SDR.	265
4H1R1	104	44002		5SDSH	265
JTH 4E11	140	44003	296	5WHRG	
JTH 4E11	141	44004	296	BL 5	146
4BP12	.262	44005	296	BLM 5	146
4H1P2	104	44006	296	LL 5	147
4H1R2	104	44007	296	LLM5	147
JTH 4E12	140	44031	296	<b>\$</b> 5	
JTH 4E12	141	44032	297	KPJ- 50	253
4H1R3	104	44033	297	ET 500	321
JTH 4E13.	140	44034	297	MM 500	312
JTH 4E13	141	44035	297	RT 500	322
JTH 4E14	140	44036	297	MM 5000.	312
JTH 4E14	141	44037	297	MM 5000N	312
4HT15	104	44100	299	VDV 500-051	53
JTH 4E15	140	44101	299	<b>VDV</b> 500-060	53
JTH 4E15	141	44103	300	500-18	125
4BP16	262	44104	299	500-24	125
JTH 4E17	140	44130	300	5003-18.	206
JTH 4E17	141	44131	300	5003-20.	206
4BP19	.262	44132	300	VDV 500-808.	54
JSD 4PH2	101	44133	300	ET 501	321
4HT20	104	44151	299	VDV 501-089.	52
42200		44200		VDV 501-809.	
42201		443A		VDV 501-814.	
42241		4BPSET5.		VDV 501-814.	
42242		KT 4500		VDV 501-815.	
42244		KT 4500		VDV 501-828	



# **I**ndex — Numerical

litem	Page	Item	Page	Item	Page
VDV 501-829.	48	5102-16.	205	VDV 512-057	51
502-10-EINS	78	5102-16SP	205	VDV 512-058.	51
D 502-10-INS		5102-18		5121-15.	
J 502-10	28	5102-18SP		5121-19.	
D 502-12		5102-20		5122-16.	
D 502-16		5102-22		5122-18.	
D 502-6.		5102-24		5124-15.	
D 503-10		5102-24SP		5124-17	
D 503-12		51028		5124-19.	
50350		5103S		5125	
50351		5104		5125L	
50355		5104S		5126.	
50400		5104VT		5127	
50402		5104CLR17		5127T	
D 504-10		5104CLR22		5129.	
D 504-10B		5105-20.		5130.	
D 504-10		5105-24		5131	
D 504-12B		5106		5136.	
D 504-7		5106P		5139.	
50500		5106S		5139B	
50500		5107-6		5139C	
50506		5107-9		5139L	
506-15		5108-18		5139L	
D 506-4		5108-20		5139PAD	
507-10		5108-24		5140	
D 507-10		5109		5140K	
507-12		5109P		5141	
D 507-12		5109PS		5141P	
507-6		5109S		5142	
D 507-6		5109SLR		5142P	
507-8		5110-48		51425	
D 507-8		5111		51427	
D 509-8		511-10		51428	
50992		D 511-10		51429	
51A		5112		5143	
51TOP		5113		5144	
5HCMH1.35		51138		5144B	
5100M		5115		5144BHB	
5101		D 511-6		5144BHHB	
5101		5118C		5144H	
51010		5118PRS		5144HBS	
51012		5118R		5144\$	
51013		5118RT		5144BHB140S	
51015	161	51188	188	5145	
51017		D 511-8		5146	
51018	161	\$ 5118PRS	187	D 514-8	21
5102S	211	5118P4	188	5CB150025	260
5102-12	205	5118P5	188	5PB150025	
5102-14	205	5119	181	5CB150030	260
5102-14SP	205	VDV 512-056	51	5PB150030	261

	Page	Item	Page	Item	Pag
5151	208	5201	196	53175	28
5152S	216	5202L	196	53176	289
5155	206	5202M	196	53177	28
5156	206	5202XL	196	53178	28
5162T	182	5204	196	5BD33	26
5163	186	5225	185	5336	20
5164	182	5225	196	53401	28
5164T	182	5236	209	53402	28
5165	182	5P0P25	263	53403	28
5CB165025	260	VDV 526-052	52	53404	28
5PB165025	261	<b>VDV</b> 526-054	54	53405	28
5CB165030	260	<b>VDV</b> 526-055	51	53406	28
5PB165030	261	D 528V	30	53407	28
5166	180	D 528V	30	53408	
5167	183	5BD30	263	53409	28
5171PS	216	5P0P30	263	53410	28
5172PS	216	5300	331	53411	28
5178		53000	288	53430	28
5179	184	53001	288	53434	28
51798	184	53002	288	53435	28
5180		53004		53436	
5CBR180022		53100		53437	
5CB180025		53101		53438	
5CBR180025		53102		53439	
5PB180025		53103		53440	
5CB180030		53104		53441	
5CBR180030		53105		53442	
5GNB180030		53106		53443	
5PB180030		53107		53444	
51810RA		53108		53445	
5182BLA		53109		53446	
51829		53110		53715	
51829M		53111		53716	
51829MHS		53112		53717	
5185.		53113		53718	
51850RA		53114		53719	
5187		53115		53720	
5187T		53116		53721	
		53117		53722	
5188				53723	
5188T		53118			
5190		53119		53725	
5194		53120		53727	
5194		53121		53728	
5195		53122		53731	
5195		53123		53732	
5195		53124		53751	
5196		53125		5P0B37516	
5196		53126		5P0B37520	
5HDRH2.0	266	53127	289	5415	190



# index — Numerica

em	Page	Item	Page	Item	Page
5415S	196	5539YEL	210	56115	159
5415XL	196	55400	191	56116	155
5416	184	55415-8	204	56116	159
5416L	184	55416-10	204	56117	161
5416T	184	55417-18	203	56118	160
5416TC	184	55418-19	203	56120	155
5416TCP	184	55419-SP		56120	159
5417	189	55421-BP	203	56125	157
5417T	189	55427	191	56203	163
5420	197	55428	191	56204	163
5420	256	55429	191		163
5420L		55452RTB			
5420S		55453HSB			
5420S		55454DHB			163
5420XL		55455M			
5420XL		55456BPL			
5425M		55460			
5425XL		55461			157
54401		5574L			159
54445		5574S			159
54446		5TL600			159
54447		56000			159
54448		56001			159
54451		56002			159
54474		5PB60020			159
54476		5P0B60020			159
54477		5PB60025			159
54484		56003			159
54486		56004			193
5PB45016		56005			138
5P0B45016		56006			138
5PRBP45016		56007			193
5P0B45020		56008			138
5456		56009			193
5456T		56010			193
5456TS		56011			106
5458.		56012			106
5459T		56013			195
5460		56014		• • • •	195
5461T		56024		• • • • • • • • • • • • • • • • • • • •	195
5471		56025			194
5481		5606			194
5482		56065			138
55		56104			152
5509		56105			152
55210		56106			152
5539BLU		56107			194
5539CPAK		56108			194
5539NAT		56110			195
5539RED	210	56115	155	5709M	195



em	Page	Item	Page	Item	Page
5709XL	195	MM 600	312	602-7DD	94
5710L	195	RT 600	322	602-8-INS	79
5710M	195	MM 6000	312	603-1	91
5710XL	195	MM 6000N	312	603-3	91
5712	152	60009	169	603-3B	95
5712	194	VDV 600-096	36	603-4	91
5713	194	600-1	91	603-4-INS	79
5714	194	60010	169	603-4B	95
5716	194	60011	169	603-6	9.
5717	195	60015	169	603-7-INS	79
5718	193	60018	170	604-3	92
5719	193	60019	170	605-4B	95
5PB75025	261	60021	170	605-6B	95
5777	208	60022	170	605-7-INS	79
58000	178	60025	170	JSD 6C06	101
58001	178	60027	170	JTH 6E06	141
58002	178	60028	170	JTH 6E06BE	14(
58003	178	60030	170	JTH 6E06BE	
58886	.208	60031	170	606-2	92
58888		60033		JTH 6E07	
58889		60034		JTH 6E07BE	
58890		60036		JTH 6E07BE	
59001		600-4		607-2	
59001T		60046		607-3	
59002		60047		607-3-INS	
5P0B90020		60049		607-4	
5PB90025		60053		JTH 6E08	
59003		60054		JTH 6E08BE	
59003T		60055		JTH 6E08BE	
59004		60056		608-2	
59005		60057		JSD 6K09	
59005T		600-6		JTH 6E09	
59008		60060		JTH 6E09BE	
59009		60060		JTH 6E09BE	
59009T		60080		610	
59011		601-10		JTH 6E10.	
59014		601-3		JTH 610E	
59014T		601-4		JTH 610E	
59031		601-4-INS		JTH 6E10BE	
				JTH 6E10BE	
59034		601-6			
59985		601-7-INS		JTH 6M10	
59990		601-8		JTH 6M10BE	
BL 6		60210B		JTH 6T10	
LM 6		60223B		610-1/4	
LL 6		602-3		610-1/4M	
LM 6		602-4		610-3/8M	
\$6		602-4-INS		610-5/16	
\$ 6H		602-4DD		610-5/16M	
<b>ST</b> 6	116	602-6	91	JTH 6E11	141



# Index — Numerica

Item	Page	Item	Page	Item	Page
JTH 6E11BE	140	630-10mm	109	632	110
JTH 6E12	141	630-11mm	109	63214	68
JTH 6E12BE	140	630-11/32	109	63218	68
JTH 6E12BE	140	630-11/32M	110	63224	68
612-4	95	63016	64	63230	68
612-4-INS	79	63020	63	63242	68
JTH 6E13	141	63028	64	633	108
JTH 6E13BE	140	630-3/16	109	63314	68
JTH 6E13BE	140	630-3/16M	110	63318	68
613-3	92	630-3/8	109	63324	68
JTH 6E14	141	630-3/8M	110	63330	68
JTH 6E14BE	140	63030	64	63336	68
614-2	92	63035	65	633-4-INS	79
614-3	92	63035SC	65	63342	68
614-4	92	630-4mm	109	633-7-INS	79
614-6	92	630-4.5mm	109	63524	69
JTH 6E15	141	63041	65	63530	69
JTH 6E15BE	140	63041TH	65	63536	69
JTH 6E15BE	140	63045	65	63542	69
JTH 6T15	143	63047	66	63607	67
JTH 6E17	141	630-5mm	109	63700	68
JTH 6E17BE	140	630-5/16	109	63711	66
618-1/4M	110	630-5/16M	110	63750	66
618-5/16M	110	630-5/8	109	63800ACSR	67
JTH 6M2	143	63050	63	63858	67
JTH 6M2BE	142	63050-EINS	77	JTH 6M4	143
JTH 6T20	143	63050-INS	74	JTH 6M4	143
620-3	92	J 63050	28	JTH 6M4BE	142
621-10	92	J 63050	63	JTH 6T40	143
621-6	92	63055	64	640-1/2	110
621-8	92	630-6mm	109	640-1/4	110
623-20	115	63060	66	640-3/16	110
623-24	115	630-7mm	109	640-3/8	110
JTH 6M25	143	630-7/16	109	640-5/16	110
JTH 6M25BE	142	630-7/16M	110	640-5/8	110
JTH 6T25	143	630-8mm	109	640-7/16	110
625-24	115	63081	65	640-9/16	110
625-32	115	630-9/16	109	64306	256
626	115	63090	65	64309	256
JTH 6T27	143	631	107	64310	256
627-20	115	631M	107	64311	256
JSD 6PH3	101	63110	66	64312	256
JTH 6M3	143	63118	68	646M	108
JTH 6M3BE		63119		646-1/2	
630M		63124		646-1/2-INS	
JTH 6T30		63125		646-1/2M	
630-1/2		63130		646-1/4	
630-1/2M		63131		646-1/4-INS	
630-1/4		63136		646-1/4M	
630-1/4M		63137		646-11/32	
000 // IIII		00101		0 10 1 1/0L	103





348

#### Item Page Page Item Item Page 646-11/32-INS 80 65620 132 65832 133 646-11/32M \_\_\_\_\_\_110 65621 132 65907 132 .....132 646-3/16 109 65622 132 65908 646-3/16-INS 80 65623 132 65909 ......132 646-3/16M \_\_\_\_\_\_110 65700 132 65910 132 646-3/8 109 65701 132 65911 132 646-3/8-INS 80 65702 132 65912 132 646-3/8M ......110 65913 132 646-5/16......109 65704 \_\_\_\_\_\_132 65914 132 646-5/16-INS 80 65705 132 65915 132 646-5/16M \_\_\_\_\_\_110 65706 132 65916 132 646-5/8 109 65707 132 65917 132 646-5/8-INS 80 65708 132 65918 132 646-7/16......109 65710 132 65919 132 646-7/16-INS ......80 JTH 6M6 ......143 646-7/16M \_\_\_\_\_\_110 65712 132 646-9/16 109 65713 132 **\$** 66 114 646-9/16-INS 80 65714 132 660 92 647 107 65715 132 661 92 647M......107 661B ......95 JTH 6M5 ......143 65717 132 66100 JTH 6M5BE 142 65720 133 661-4-INS 79 650 115 65721 133 66140 65020 116 65722 133 66142 65160 108 65723 133 66143 65500 ......131 66144..... 65502. 130 65800 133 66145 65503 ......131 66146 65504 131 65802 133 661-7-INS 79 65803 133 65506 130 66174 65508 131 65804 133 66177 ..... 66183 ..... 65512 130 65806 133 662 92 662B 95 662-4-INS 79 65600 132 65808 133 65601 132 65809 133 662-7-INS 79 65810 \_\_\_\_\_\_133 663 92 65603 132 65811 133 66310 ..... 65604 132 65812 133 66311..... 65605 132 65820 133 66312 65606 132 65821 133 66313 65607 \_\_\_\_\_\_132 65822 133 66320 66321 65610 132 66322 66323 65612 132 65827 133 66324 65613 132 65828 133 66325 .307 65614 132 65829 133 66340 65830 \_\_\_\_\_\_133 66342 ..... 66343 .....

# Index - Numerica

Item	Page	Item	Page	Item	Page
66344	307	68415	127	69406	192
66385	115	68416	127	69406	326
66400	274	68417	127	69407	192
665	92	68418	127	69407	326
JTH 67T	143	68419	127	69408	192
670-3	93	68420	127	69408	326
670-6	93	68421	127	69410	323
67100	93	68422	127	69411	323
67101	93	68423	127	69412	324
67101	98	68424	127	69413	324
671-6	93	68425	127	69414	324
JTH 68M	142	68450	129	69415	323
JTH 68MB.	142	68452	129	69450	
JTH 6M8	143	68460	129	69451	324
JTH 6M8BE	142	68461	129	69454	
68005	32	68462	129	69455	324
68005	135		129	69457	
	93		129	BL7	146
	134		129	DS 7	
	134		129	K7	
	134		128	LL7	
	134		128	<b>\$</b> 7	
	134		128	70	
	134		128	\$700	
	134		128	70035	
	134		128	70084	
	134		128	701-S	
	135	• • • • • • • • • • • • • • • • • • • •	128	701-10	
	135		128	701-12	
	135		128	702	
68240	135	68515		70200	
	135		128	70204	
	134		128	70205	
	135		322	70206	
	93		322	70207	
	135		323	70208	
	276		322	70209	
	135		322	70210	
	276		322	70211	
	135		323	702-12	
	276		323	70220	
	126		93	70245	
	126		325	70255	
	127		312	70233	
	127		312	703	
	127		312	7HBRFRH04	
	127		312	705	
	127		93	70570	
	127		325	70571	
68414	127	69401	326	70572	144



70573 ......144

Page

Item

Page

76012B ......272

**VDV** 770-050......41

Item

VDV 814-633......44

VDV 814-634......44

Page

Item



		1
		I
		/

70575	144	VDV 770-080	51	VDV 814-635	44
70579	144	BL 8	146	VDV 814-636	44
70580	144	BLM 8	146	<b>VDV</b> 814-637	44
70581	144	LL 8	147	VDV 814-638	44
70582	144	LLM 8	147	<b>S</b> 818	114
70583	144	<b>\$</b> 8	114	<b>S</b> 818M	114
70586	144	<b>S</b> 8M	114	<b>S</b> 818M	114
70591	144	<b>SS</b> 8	113	818-16	305
706	293	80014	331	818-20	305
707	293	80028	329	820-16	277
7HBRFRH07	266	80118	330	820-16	306
709	293	80141	328	821-12	277
7HBRFRH10	266	803-12	305	821-12	306
7FWSS10025	263	803-16	305	823-48	305
7SC120019	262	803-24	305	VDV 824-632	45
7WRP13	267	803-32	305	VDV 826-600	45
7HBRFRH14	266	803-8	305	VDV 826-601	45
7SC150019	262	807-18	305	VDV 826-602	45
7CHC15013	262	808-16	305	VDV 826-603	45
7WRP16	267	808-20	305	VDV 826-604	45
PND 71610	121	809-36	306	VDV 826-605	45
PND 7165	121	809-36MF	306	VDV 826-611	45
7CHC17516	262	811-16	277	VDV 826-628	45
7SCT1800	261	811-16	306	832-32	305
7SCTH1800	261	811-32	277	85071	90
7SC180019	262	811-32	306	85072	90
7WRP19	267	VDV 812-606	43	85074	88
71980	30	VDV 812-612	43	85075	88
71980	31	VDV 812-615	43	85076	87
7CHC20020	262	VDV 812-618	43	85077	87
7SC210019	262	VDV 812-623	43	85078	87
72192	30	VDV 812-624	43	85091	94
72192	30	VDV 812-625	43	85091	120
7WRP22	267	VDV 812-626	43	85105	88
7SCTH2400	261	VDV 812-627	43	85155	90
7SC240019	262	VDV 813-607	43	85191	94
725	293	VDV 813-608	43	85191	162
7WRP25	267	VDV 813-613	43	85276	102
7BP29219	262	VDV 813-614	43	85484	89
7BP29225	262	VDV 813-616	43	85614	89
7BP29232	262	VDV 813-617	43	85664	90
7WRP32	267	VDV 813-619	43	<b>S</b> 86	114
7SCT3660	261	VDV 813-620	43	<b>S</b> 86M	114
74007	58	VDV 814-609	44	86550	275
74017	60	VDV 814-610	44	86551	272
7SCT4320	261	VDV 814-629	44	86552	272
<b>KPJ-</b> 75	253	VDV 814-630	44	86553	272
76011B	272	VDV 814-631	44	86554	273

JTH 9E08......141

m	Page	Item	Page
86555	273	JTH 9E09	140
86556	272	JTH 9E09.	141
86560	272	JTH 9E10	140
86570	276	JTH 9E10	141
86571	276	JTH 910E	140
86600	275	JTH 910E	141
86600-10	275	JTH 9M10	143
86601	275	910-6	152
86601-10	275	JTH 9E11	140
86602	275	JTH 9E11	141
86602-10	275	911-6	152
87904		JTH 9E12	
87906		JTH 9E12	
88904		JTH 9F13	
88905		JTH 9F13.	
88906		JTH 9E14.	
88975		JTH 9F14.	
88976		JTH 9E15.	
88977		JTH 9E15.	
88978			
		PND 91610	
88980		PND 9165	
88981		JTH 9E17	
88982		JTH 9E17	
89		JTH 9M2	
8900-1/2		92003	
8900-3/8		JTH 9M25	
89004		928-16HV	
89018		928-25HV	
89019		JTH 9M3	
89020		93025	
89021	274	930-9	149
89025	274	93116	151
89030	273	93125	151
8910-1/2	275	931-6RE	149
8910-3/4	275	9317RE	150
89565	275	931-9RE	149
89904	113	93225	151
89969	111	93275	151
L9	146	932-9RE	149
L9	147	9330RE	150
<b>\$</b> 9	114	93430	151
900-6	152	946-100.	153
901-6	152	946-150.	153
905-6	152	946-50	153
H 9E06		JTH 9M5	
H 9E06	141	JTH 9M6	143
H 9E07		JTH 98M	
H 9E07		JTH 9M8	
H 9E08		VDV 999-033.	
II JLUU	140	000-000	42



Page

. 136

Item

NRHDA....



# Important information for everyone who uses hand tools...fully illustrated pages of basic facts and practical "how-to" tips.



The warranty information on this page may only be applicable in the US and Canada. See www.kleintools.com/warranty for more information.

#### Warranty

Klein products in this catalog, manufactured and sold for commercial or industrial uses, are warranted to be free from defects in materials and workmanship for the normal life of the product, with the exception of: I. Electronic Test & Measurement products (see warranty below); and II. Ratcheting and Drill-Operated Cable Cutters, which are warranted for one year from the date of purchase. The following consumable products are warranted to be free from defects in materials and workmanship when delivered to the customer: Triple-Taps, Drill Bits, Step Drills, Carbide Hole Cutters, Hole Saws and Arbors; Saw Blades and Jab Saws; disposable Razor and Knife Blades; Stripper Cartridges, Replaceable Cutting Inserts, Bits and Blades; Hand Cleaners and Wire Pulling Lubricant. THERE ARE NO IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS. At its option Klein will repair or replace, or refund the purchase price of, any product which fails to conform to this warranty under normal use and service. In no event shall Klein be liable for incidental or consequential damage.

If your Klein product requires repair or for information on how to exercise your rights under the terms of this warranty, please contact **Klein Tools at 1-800-553-4676.** 

#### **Electronic Test & Measurement Warranty**

Klein electronic test and measurement devices (and accessories), manufactured and sold for commercial or industrial uses, are warranted to be free from defects in materials and workmanship for two years from the date of purchase (unless otherwise noted on the product packaging). THERE ARE NO IMPLIED WARRANTIES OF MERCHANTIBILITY OR FITNESS. At its option, Klein will repair or replace, or refund the purchase price of, any product which fails to conform to this warranty under normal use and service. In no event shall Klein be liable for incidental or consequential damage. This warranty does not apply to batteries.

#### **Warranty Returns**

All warranty returns must include a Warranty Return Authorization (WRA) number. The WRA for the U.S. can be obtained by calling Customer Service at 1-800-553-4676. (International call 1-847-821-5500) or email serviceonline@kleintools.com.

#### Specifications of all products in this catalog are subject to change without notice.

Dimensions shown for all forged products in this catalog are as precisely accurate as possible, but subject to very slight variations that are unavoidable in forging and grinding operations. Dimensions of Klein forged tools and all other tools and equipment are always within commercial tolerances recognized for such products.







Lincolnshire • IL

## **Committed to American Manufacturing Since 1857**



Mansfield • TX



Cedar Rapids • IA



Fort Smith • AR



Elk Grove • IL



Rockford • MI



Bolivar • NY





