

BRK[®]

THE PROFESSIONAL STANDARD

Product Catalog

Distributor

Volume 15

SMOKE ALARMS

CO ALARMS

COMBO ALARMS

HEAT ALARMS

LEADERS IN RESIDENTIAL & MULTI-FAMILY ALARM TECHNOLOGY



Onelink™

Suite of Connected Products

In 2015, First Alert will roll out the new Onelink™ suite of connected products that cover categories including home environment monitoring, fitness, safety and security. Onelink™ transcends current perceptions of safety products to usher in a new era of accessibility and customization.

From a watch that acts as a personal wellness and protection device to an environment sensor, smoke and carbon monoxide alarm, safe and tracking device that can talk to your smartphone, First Alert is bridging the gap between connected home products and mobile security with a new series of smart devices aimed at simplifying and enhancing people's comfort, safety and peace of mind. Products in the new First Alert Onelink™ collection operate exclusively with iOS® devices, and are designed to seamlessly integrate with one another to create a comprehensive smart home that can be controlled and monitored from virtually anywhere by a user's mobile device.

Fitness/Security Watch



This Bluetooth-enabled watch is ready to change your life. Tracks to your custom health/fitness goals, automatically detects activity, continuously monitors heart rate with no chest strap, records workout sessions, automatically measures sleep (REM, light & deep) and sends safety alerts with GPS location. Flaunting a gorilla glass, vibrant OLED display with easy, touch-swipe navigation, this watch wakes simply by raising the wrist. It's IP67 waterproof and features interchangeable bands to suit your active lifestyle.



SKU #'s:
WATCH-500SSBS (Black Band)
WATCH-500SSWS (White Band)

Tracker




Help keep your valuable tools and personal items safe and within reach with Onelink Tracker. Bluetooth/iBeacon technology means that when tagged items are in motion or out of range, your Onelink Tracker will send instant notifications, alarms and offer a 911-call option from your connected smartphone or tablet. The mounting strap accessory conveniently attaches the device to handles, valuables and equipment. Using the free app, set safes zones to track or locate your personal property.



SKU #: TRACKER-500

Wi-Fi Environment Monitor



Detect carbon monoxide (CO) in your home or office with this low-level CO environment monitor. Built-in temperature and humidity sensors with a multi-color LED ring to indicate immediate temperature shifts add an extra level of security. Receive notifications or check changes in the room temperature, humidity and carbon monoxide levels from your smartphone or tablet
(Note: Low Level CO Monitor. Not a UL 2034 CO Alarm)




SKU #: GLOCO-500

First Alert

Onelink™

Wi-Fi Smoke & Carbon Monoxide Alarm



SKU #'s:
AC10-500B (120V Hardwired
w/ Battery backup)
DC10-500B (Battery Powered)



Connected



Smoke & Fire



Carbon
Monoxide



Voice w/
Location



Free App



AC/DC

A 2-in-1 combination Smoke and Carbon Monoxide alarm equipped with a 10 Year battery that lasts the life of the alarm. No more annoying low battery chirps in the middle of the night. No wobbling on a ladder to replace batteries. Premium protection that just works.

Features

- Smoke & CO Combo Alarm
- Two versions: Hardwired and battery operated
- Wi-Fi and Bluetooth connectivity
- 10 Year battery or battery backup
- Free App to stay connected with alarms
- Voice with location
- Interconnects with all BRK/First Alert hardwired alarms



Wi-Fi Safe



Connected



Fireproof



Waterproof



5-Year
Warranty



Free App



Bolt-Down
Security

Easily lock and unlock your Wi-Fi connected and Bluetooth-enabled safe right from your smartphone or tablet without the need for passcodes or keys. Customize settings, add personalized notifications, and grant remote access to friends and family, as well as monitor their activity, by conveniently connecting to the mobile app. Sleek new design with aluminum alloy handle and LED light that signals when safe is unlocked, locked or tampered with. No key pad and no dials = no forgotten passcodes. Your phone is your key. And never get locked out with emergency USB power boost backup when batteries have lost power.

SKU #'s:
2096BD-500 (2.1 cu ft)
2092BD-500 (1.3 cu. ft)

BRK®

THE PROFESSIONAL STANDARD



WIRELESS INTERCONNECT

Cost Effective Retrofit & Remodel Solutions

- Wireless interconnect technology eliminates the need to pull wires through existing walls
- Save an average of between \$150 - \$200** per alarm when compared to retrofitting hardwired alarms in existing walls or ceilings
- Faster job turnaround - 4X more jobs completed increases your profits
- Photoelectric sensing technology saves maintenance calls with fewer nuisance alarms

Putting the Innovation in Renovation

When it comes to alarm renovation and retrofit projects, choices have been limited. Installing battery operated alarms and sacrificing interconnectability or investing in the time and labor to retrofit hardwired alarms have been the only options available.* Until Now! BRK Wireless Interconnect eliminates the need to pull wires through existing walls saving time, money and labor.

No matter what your renovation project, BRK Wireless Interconnect provides a cost effective solution:

Home Addition Projects:

Using the BRK Wireless Interconnect hardwired "Bridge Unit" (SA520B), simply replace one hardwired alarm in the existing section and add one to the new section. Wireless technology saves time, material and labor to connect to the existing alarm circuit. Now add standard BRK hardwired alarms as required in the new section and other BRK Wireless Interconnect battery alarms in the old section to complete the alarm safety system and bring entire home up to code. All alarms, hardwired and battery, existing and new are now interconnected.

Retrofit Projects:

Property Owners, Facility Managers and Electrical Contractors can all benefit from installing BRK Wireless Interconnect alarms for existing retrofit projects. Saving \$150 - \$200** per alarm and increasing job turnaround 4X are key reasons to consider BRK Wireless Interconnect alarms for all of your renovation projects.


Mesh Network Communication

BRK Wireless Interconnect alarms operate on a "mesh network"; a 2-way communication format that sends, receives and then re-sends the alarm signals. If the initiating alarm signal is blocked from reaching one of the alarms, the mesh network communication reroutes and re-sends the signal via the other alarms as shown in the illustration. With competitive one-way wireless communication, only the initiating alarm sends a signal which may never be received, leaving the blocked alarm deadly silent.

*Local codes permitting

**Note: Based on average retrofitting costs of time, material and labor to connect to existing alarm circuit, drywall repairs, painting, etc. Special cases that require conduit, wire mold, concrete drilling, etc. would add additional costs and increase savings.


This product is intended for non-professional do it yourself installation. If you would like information about a professionally installed and monitored system, please contact First Alert Professional at 1-800-921-6025. First Alert Professional is not affiliated with BRK Brands, Inc.



BRK®
THE PROFESSIONAL STANDARD

**WIRELESS
INTERCONNECT**

Mesh Network Communication



**Competitive Wireless
One-Way Communication**

Innovative Features

WIRELESS INTERCONNECT

Reliable and secure radio frequency communication between alarms. 915 MHz frequency with 65,000 security codes and 3 channel frequency hopping.

MESH NETWORK COMMUNICATION

2-way communication format that sends, receives and re-sends the alarm signals providing a more reliable network.

VOICE WARNING WITH LOCATION

Exclusive! Programmable with up to 11 locations (ex. "basement"). When alarm sounds (if programmed for basement), it will say, "Warning, Evacuate, Smoke in Basement". If other BRK Wireless Interconnect Voice Warning alarms are located throughout the house they will also signal, "Warning, Evacuate, Smoke in Basement".

PHOTOELECTRIC TECHNOLOGY

Helps reduce nuisance alarms, especially around kitchens and baths which are more prone to nuisance alarms from cooking smoke and shower steam.

OPTIPATH 360 TECHNOLOGY™

Patented technology provides 360 degrees of direct access to smoke sensor.

SPREAD SPECTRUM HORN TONE

Lower and varying horn frequency makes it easier for elderly with normal age related hearing loss to hear horn. Sweeps through the 2200 - 3400 Hz range.

LATCHING FEATURES

Alarm Latch: Easily identifies initiating alarm even after alarm condition has subsided. **Low Battery Latch:** Identifies which unit is in low battery condition. Both features activate for up to 15 minutes. (excludes SA520B).

SILENCE FEATURE

Silences unwanted alarms. Two silence features - Temporarily silence low battery chirp for up to 8 hours before replacing battery or silence unwanted alarm for several minutes.

SCO500B - Battery Smoke/CO Combo



WIRELESS PHOTOELECTRIC & ELECTROCHEMICAL CO BATTERY POWERED

- Easily add Smoke/CO Combo alarms outside bedrooms and on every level of the home to create a wireless safety network.

Exclusive!
Voice Warning!
WITH LOCATION



SA511B - Battery Smoke Alarm



WIRELESS PHOTOELECTRIC BATTERY POWERED

- Easily add smoke alarms to every bedroom to create a wireless safety network.

Exclusive!
Voice Warning!
WITH LOCATION



SA520B - Hardwired Smoke Alarm



BRIDGE UNIT - WIRELESS PHOTOELECTRIC 120V WITH BATTERY BACKUP

- Easily expand an existing interconnected 120V AC system by replacing one alarm in the series with this Bridge Unit alarm.
- Add additional battery-operated BRK Wireless Interconnect Alarms to create a wireless safety network.



CO511B - Battery CO Alarm



WIRELESS ELECTROCHEMICAL CO BATTERY POWERED

- Easily add CO alarms outside bedrooms and on every level of the home to create a wireless safety network.

Exclusive!
Voice Warning!
WITH LOCATION



HARDWIRED SMOKE ALARMS



9120 SERIES

120V AC WITH BATTERY BACKUP - ION

- Ionization smoke sensing technology
- Silence Feature
- Latching alarm indicator – remembers which unit initiated an alarm
- Smart Technology – helps reduce the number of nuisance alarms
- Perfect Mount – allows for easy alignment of alarm
- 9V battery backup (excludes cat. no. 9120)

Available SKU's:

- 9120: AC only
- 9120B: AC with 9V battery backup
- 9120AB: AC with 9V Alkaline battery backup
- 9120LBL: AC with 10YR 9V Lithium battery backup - Locked Battery Drawer
- 9120B6CP: 9120B in bulk Contractor 6-pack

9120 Series –
"The smoke alarm
standard of excellence".
9120LBL features a 10YR
battery backup with a
locked battery drawer.



3120B

120V AC WITH BATTERY BACKUP - ION & PHOTO

- Dual photoelectric and ionization smoke sensing technologies
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition
- Two AA alkaline battery backup

Tip:
Combination Photo & Ion
smoke alarms meet
codes in Massachusetts and
Iowa.



7010 SERIES

120V AC WITH BATTERY BACKUP - PHOTO

- Photoelectric smoke sensing technology
- Silence Feature
- Alarm Latch: Remembers which unit initiated an alarm.
- 9V battery backup (excludes cat. no. 7010)
- Escape light illuminates path to safety (cat. no. 7020B)

Available SKU's:

- 7010: AC only
- 7010B: AC with 9V battery backup
- 7020B: AC with 9V battery backup & escape light

Tip:
Recommended for installation
outside areas that are prone to
nuisance alarms such as
kitchens, bathrooms and
utility rooms. Escape light
recommended for hallway
applications.



7020B

HARDWIRED COMBO ALARMS

7010BSL

120V AC WITH BATTERY BACKUP - PHOTO/STROBE COMBO

- Photoelectric smoke sensing technology
- Silence Feature
- Bright 177 candela strobe light designed for hearing impaired residents
- Smart Strobe has separate flash patterns to distinguish between a smoke/heat or CO danger
- Two AAA battery backup for smoke alarm. (Note: will not power strobe light)
- Meets the requirements of the ADA (Americans with Disabilities Act)
- 1Hz flash rate meets requirements for visual signaling devices



Tip:
Integrated smoke alarm and strobe light saves installation time and money compared to other manufacturers' hearing impaired kits that require a separate alarm, relay and strobe light.



SC7010 SERIES

120V AC WITH BATTERY BACKUP - PHOTO/CO COMBO

- Voice Warning with Location – Exclusive! A voice will tell you the programmed location of unit and the danger detected (cat. no. SC7010BV)
- Advanced electrochemical CO and photoelectric smoke sensing technologies
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- 10 Year CO Sensor/End of Life signal
- Two AA battery backup

Available SKU's:

- SC7010B: Smoke/CO Combo
- SC7010BV: Smoke/CO Combo with Voice



Exclusive!
Voice Warning!
WITH LOCATION™



Tip:
Combination alarms save time and money on installation.

SC9120B

120V AC WITH BATTERY BACKUP - ION/CO COMBO

- Advanced electrochemical CO and ionization smoke sensing technologies
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Intelligent Sensing Technology™ – helps reduce the number of nuisance alarms
- 10 Year CO Sensor/End of Life signal
- 9V battery backup

Available SKU's:

- SC9120B: AC with 9V Alkaline battery backup
- SC9120LBL: AC with 10YR 9V Lithium battery backup - Locked Battery Drawer



SC9120LBL features a 10YR battery backup with a locked battery drawer.



HARDWIRED CO ALARMS/MISCELLANEOUS



CO5120BN

CO5120 SERIES

120V AC WITH BATTERY BACKUP - ELECTROCHEMICAL

- Advanced electrochemical CO sensing technology
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition
- 10 Year CO Sensor/End of Life signal
- 9V battery backup
- LCD display - clearly shows the hazard and level (cat. no. CO5120PDBN)



CO5120PDBN



MISCELLANEOUS

HD6135FB


120V AC WITH BATTERY BACKUP - HEAT ALARM

- 135°F Fixed temperature and Rate-of-Rise Thermistor heat sensor
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Latching alarm indicator – remembers which unit initiated an alarm
- 10 Year End of Life signal
- 9V battery backup
- For applications not suitable for smoke alarms



Understanding Rate of Rise

This allows the unit to sense a heat rise and alarm prior to reaching the fixed temperature. The alarm will sound when the microprocessor senses a temperature rise of a set number of degrees per minute. This enables a more rapid response to a potential fire.



SL177

120V AC - SMART STROBE

- Smart Strobe has separate flash patterns to distinguish between a smoke/heat or CO danger
- Bright 177 candela strobe light
- 1Hz flash rate meets ADA, ANSI 117.1, NFPA 72 and UL 1971 requirements for visual signaling devices
- Can be interconnected with BRK/First Alert smoke, heat and carbon monoxide alarms



Product Knowledge:
What's a "Smart Strobe"?
Separate flash patterns help a hearing impaired person better distinguish the danger present.
Smoke or Heat Alarms: Constant 1 flash per second for 4 flashes, then 5 seconds off. Pattern is repeated.

PLUG-IN CO ALARMS

CO600 SERIES

120V AC PLUG-IN WITH BATTERY BACKUP -
ELECTROCHEMICAL

- Advanced Electrochemical CO sensing technology
- Silence feature - temporarily silence an unwanted nuisance alarm
- 7 Year CO Sensor/End of Life signal
- Battery Backup Options:
9V battery backup: CO605B
Two AA battery backup: CO615B
No battery backup: CO600B
- Battery Access
Rear Panel: CO605B
Front Panel: CO615B
- LCD display - clearly shows the hazard and level: CO615B
- CO615B features convenient installation options. Alarm plugs directly into the outlet or can be mounted anywhere on the wall using the 6' line cord



Multi-family Manager Tip:
First Alert alarms with AA
batteries save 33% on annual
battery replacement costs vs. 3
for competitive products.



CO600B &
CO605B

Multi-family Manager Tip:
9V batteries are less prone
to tenant theft for use in other
electronic devices due
to their infrequent usage by
manufacturers.

GCO1B

10YR SEALED BATTERY POWERED -
EXPLOSIVE GAS & ELECTROCHEMICAL

- 3-way protection against natural (methane) gas, propane gas and carbon monoxide.
- Large display - clearly shows the hazard and level present
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Convenient Installation Options: unit plugs directly into the wall or can be mounted higher on the wall using the line cord
- 5 Year Explosive gas & CO Sensors/End of Life signal
- 9V battery backup



BATTERY SMOKE ALARMS



Actual Size Approximately
(1-5/8" H x 1-7/8" Dia)



P1000/P1010

BATTERY POWERED MICRO - PHOTO

- Advanced Photoelectric Micro Technology
- Maximum Protection - Fewer False Alarms
- Easy Installation - Smart Product Clip System

Available SKU's:

- P1000: Long life lithium battery
- P1010: 10YR sealed lithium battery



SA320B/SA3210

BATTERY POWERED - ION & PHOTO COMBO

- Dual photoelectric and ionization smoke sensing technologies
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition

Available SKU's:

- SA320B: Two AA battery operated
- SA3210: 10YR sealed battery in clamshell



Tip:
Combination Photo & Ion
smoke alarms meet
codes in Massachusetts and
Iowa.



PR700 SERIES

BATTERY POWERED - PHOTO

- Low profile slim design
- Photoelectric smoke sensing technology
- Silence feature
- 9V battery included

Available SKU's:

- PR700B: 9V carbon zinc battery operated
- PR700AB: 9V alkaline battery operated
- PR700LB 9V lithium battery operated
- PR700E: 9V carbon zinc battery operated with escape light



BATTERY 10YR SEALED ALARMS

PRC710VB

10YR SEALED BATTERY POWERED - PHOTO/CO COMBO

- Low profile slim design
- 10 Year sealed lithium powercell prevents battery theft
- Tamper proof design
- Advanced electrochemical CO and photoelectric smoke sensing technologies
- Voice Warning with Location – Exclusive! A voice will tell you the programmed location and the danger detected
- Silence Feature
- 10 Year CO Sensor/End of Life signal



Tip:
Never Change a Battery Again!
Saves battery replacement
and maintenance costs.
Recommended for multi-family
and dormitory applications

Exclusive!
Voice Warning!
WITH LOCATION



PRC710B

10YR SEALED BATTERY POWERED - PHOTO/CO COMBO

- Same as PRC710VB without Voice Warning feature



PRC710B

PR710B

10YR SEALED BATTERY POWERED - PHOTO

- Low profile slim design
- 10 Year sealed lithium powercell prevents battery theft
- Tamper proof design
- Photoelectric smoke sensing technology
- Silence Feature
- 10 Year End of Life signal



PR710B

CO910 SERIES

10YR SEALED BATTERY POWERED - ELECTROCHEMICAL CO

- Low profile slim square design
- 10 Year sealed lithium powercell prevents battery theft
- Tamper proof design
- Advanced CO sensing technology
- Silence Feature
- Voice Warning with Location – Exclusive! A voice will tell you the programmed location of unit and the danger detected (cat. no. CO910VB)
- 10 Year CO Sensor/End of Life signal

Available SKU's:

- CO910B: CO alarm
- CO910VB: CO alarm with Voice



CO910B

CO910VB

Exclusive!
Voice Warning!
WITH LOCATION

BATTERY CO ALARMS



CO250 SERIES

BATTERY POWERED - ELECTROCHEMICAL CO

- Advanced Electrochemical CO sensing technology
- Hinged cover for easy battery replacement
- Lighted Power and Alarm indicator
- Silence Feature
- Tamper resistant locking pin
- 9V battery powered
- 10 Year CO Sensor/End of Life signal

Available SKU's:

- CO250B: Alkaline battery
- CO250LB: 5 year Lithium battery
- CO250LBT: Lithium battery; Tamper Proof



*Multi-family Manager Tip:
9V batteries are less prone
to tenant theft for use in other
electronic devices due
to their infrequent usage by
manufacturers.*



CO250LBT

CO250 w/TAMPER PROOF BRACKET

- Uses CO250LB lithium battery CO alarm from above
- Tamper proof bracket locks alarm to wall with a tamper proof screw
- Tamper proof spanner screw and screwdriver bit included
- 5 year 9V lithium battery
- 10 Year CO Sensor/End of Life signal



CO710

BATTERY POWERED - ELECTROCHEMICAL CO

- 10 Year sealed lithium powercell prevents battery theft
- Large display - shows visual confirmation of CO levels
- Advanced CO sensing technology
- Silence Feature
- 10 Year CO Sensor/End of Life signal



CO400B



CO400B/CO410B

BATTERY POWERED - ELECTROCHEMICAL CO

- Advanced Electrochemical CO sensing technology
- Silence Feature
- 9V battery powered
- 7 Year CO Sensor/End of Life signal
- CO410B: Same features as above plus or instead of
 - Large display - shows visual confirmation of CO levels
 - 2 AA battery powered



*Multi-family Manager Tip:
First Alert alarms with AA
batteries save 33% on annual
battery replacement costs vs. 3
for competitive products.*

CO410B

BATTERY SMOKE & CO COMBO ALARMS

SCO2 SERIES

BATTERY POWERED - ION/CO COMBO

- Advanced electrochemical CO and ionization smoke sensing technologies
- Two Latching features – Alarm Latch: Remembers which unit initiated an alarm. Low Battery Latch: Identifies which unit is in low battery condition
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- 10 Year CO Sensor/End of Life signal; 9V battery powered

Available SKU's:

- SCO2B: Alkaline battery
- SCO2LB: Lithium battery



ZCOMBO-G

BATTERY POWERED - PHOTO/CO COMBO

- Communicates with any Z-Wave technology wireless hub.
- Advanced electrochemical CO and photoelectric smoke sensing technologies
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- 10 Year CO Sensor/End of Life signal; Two AA battery powered



Product Knowledge:
This alarm connects to any wireless hub featuring Z-Wave technology. This alarm will not connect to Onelink or BRK Wireless Interconnect alarms.

PRC700VB

BATTERY POWERED - PHOTO/CO COMBO

- Voice Warning with Location: Exclusive! A voice will tell you the programmed location of unit and the danger detected.
- Advanced electrochemical CO and photoelectric smoke sensing technologies
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- 10 Year CO Sensor/End of Life signal
- Two AA battery powered



Tip:
"Voice with Location" provides necessary hazard location information for blind or visually impaired residents.

Exclusive!
Voice Warning!
WITH LOCATION™



PRC700B

BATTERY POWERED - PHOTO/CO COMBO

- Advanced electrochemical CO and photoelectric smoke sensing technologies
- Two silence features – can silence the low-battery chirp for up to eight hours or temporarily silence an unwanted nuisance alarm
- 10 Year CO Sensor/End of Life signal
- Two AA battery powered



BATTERY SMOKE ALARMS



SA350B

10YR SEALED BATTERY POWERED - ION

- 10 Year sealed lithium powercell prevents battery theft
- Tamper proof design
- Perfect Mount – allows for easy alignment of alarm
- Silence feature



Tip:
Never Change a Battery Again!
Saves battery replacement
and maintenance costs.
Recommended for multi-family
and dormitory applications



FG250 SERIES

BATTERY POWERED - ION

- Hinged cover for easy battery replacement
- Lighted Power and Alarm indicator
- Silence feature
- Tamper resistant locking pin
- RV approved (FG250AB & FG250LB)
- 9V battery powered

Available SKU's:

- FG250B: Carbon zinc battery
- FG250AB: Alkaline battery
- FG250LB: Lithium battery



The most feature rich
alarm in its class.

SA303B/SA305B



SA304CN

SA300 SERIES

BATTERY POWERED - ION

- Silence feature
- Hinged battery drawer for easy battery replacement
- Lighted Power and Alarm indicator
- Tamper resistant locking pins
- 9V battery powered
- Model SA304CN features an Escape light that illuminates path to safety

Available SKU's:

- SA303B: Carbon zinc battery
- SA305B: Lithium battery
- SA304CN: Alkaline battery w/ escape light



OTHER MISCELLANEOUS

EL52-2/EL53W-2

ESCAPE LADDERS

- Strong steel construction with Slip-resistant rungs
- Large hooks secure easily to widow sills
- DuPont Cordura™ Nylon Strapping
- Fully assembled and ready to use
- Tested to ASTM standards

Available SKU's:

- EL52-2 Two-story 14 foot long
- EL53W-2 Three Story 24 foot long



PIR725

MOTION SENSOR

- Motion sensing hands-free socket automatically turns on light when you enter room and off when you leave
- Installs in existing light socket
- Senses movement in all directions (12-foot range 360°)
- Works with incandescent bulbs up to 100 watts or compact fluorescent bulbs up to 50 watts



RM4

RELAY

- For BRK smoke and "smart interconnect" CO alarms
- 120-volt AC-powered
- Form-C contacts that switch between normally open and closed contacts
- Maximum contact rating: 120-volt AC and 30-volt DC; Resistive-15 amps; Motor-1/3 horsepower




ADF-12/ADK-12

ADAPTOR PLUGS

- Easily connect competitive alarms without rewiring
- For use with select Firex® and Kidde® smoke alarms
- Perfect for retrofit applications

Available SKU's:

- ADK-12 Kidde® adaptor
- ADF-12: Firex® adaptor



LEADERS IN RESIDENTIAL & MULTI-FAMILY ALARM TECHNOLOGY

BRK[®]

THE PROFESSIONAL STANDARD

©2015 BRK Brands Inc.
a Jarden Corporation Company (NYSE: JAH)
3901 Liberty Street Road, Aurora, IL 60504-8122
Customer Service: 800-275-2576 Tech Services: 800-323-9005
All rights reserved
First Alert is a registered trademark of the First Alert Trust
BRK is a registered trademark of BRK Brands, Inc.
www.brkelectronics.com
CM3229