


Superstrut®

**Metal Framing,
Channel, Fittings,
Pipe Straps and
Beam Clamps**



2008 Edition



• ISO 9001 : 2000 REGISTERED MANUFACTURER •

Thomas & Betts is dedicated to improving its already high quality standards. To date, we have achieved ISO 9001 : 2000 certification for more than 50 plants and distribution centers worldwide and continue to commit resources to the ISO certification program.

WARRANTY

Thomas & Betts manufactures its goods and tools in a manner to be free from defects. Should any defect occur in its goods (within two years) or tools (within ninety days), Thomas & Betts, upon prompt notification, will at its option, exchange or repair the goods or tools or refund the purchase price.

LIMITATIONS AND EXCLUSIONS

THIS WARRANTY IS IN LIEU OF ALL OTHER REPRESENTATIONS, CONDITIONS AND WARRANTIES, EXPRESSED OR IMPLIED, STATUTORY OR OTHERWISE (INCLUDING STATUTORY IMPLIED CONDITIONS AND WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE) AND UNDER NO CIRCUMSTANCES SHALL THOMAS & BETTS BE LIABLE FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES OR LOSSES, INCLUDING, WITHOUT LIMITATION, PERSONAL INJURY CAUSED BY IMPROPER USE OR APPLICATION OF ANY THOMAS & BETTS PRODUCT.

TABLE OF CONTENTS

FINISHES AND MATERIALS.....	5
SECTION 1 - CHANNELS AND CONCRETE INSERTS 7	
Channels	8
Welded Combinations	10
End Caps and Closure Strips	10
Concrete Inserts.....	11
SECTION 2 - THREADED PRODUCTS AND HARDWARE 13	
Threaded Rod and Accessories	14
SECTION 3 - FITTINGS AND BRACKETS 19	
Flat Fittings.....	20
90° Fittings	21
Angular Fittings	23
“Z” Shape Fittings	23
“U” Shape Fittings	24
Wing Fittings	25
Brackets	26
Post Bases	28
Special Application Fittings and Brackets	29
SECTION 4 - BEAM CLAMPS 31	
Beam Clamps for Mounting Channel	32
Beam Clamps for Hanging Rod	34
Beam Clamps for Mounting Pipe and Conduit.....	37
Beam Fittings	38
SECTION 5 - PIPE STRAPS, PIPE CLAMPS AND HANGERS 41	
Conduit and Cable Clamps	42
Pipe Hangers	51
Seismic Bracing	54
Hanger Accessories	55
SECTION 6 - SURFACE RACEWAY AND LIGHTING SYSTEMS 57	
Fixture Fittings	58
Kindorf® Channel Boxes and Receptacles	60
Kindorf® Fixture Accessories	61
Electrical Applications	61
SECTION 7 - RIGHT ANGLE SLOTTED METAL FRAMING 65	
SECTION 8 - ENGINEERING DATA AND SPECIFICATIONS 69	
ALPHANUMERIC INDEX 86	

Superstrut®

Finishes and Materials

FINISHES ON STEEL

Bare (Suffix BC)

Pregalvanized (Suffix PGC)

A zinc coating is applied by hot-dipping the steel coil at the mill prior to fabrication. Once the material is worked by roll-forming, cutting, or punching, minimal protection is provided for raw edges. This weakness is typical with precoated material and affects the channel section around holes, extreme ends, and the edges of the U-shape lips. Superstrut® pregalvanized material is in conformance with ASTMA-525/G-90 specification standards, representing 0.90 oz. of zinc per square foot of steel. This finish is often referred to as "hot-dipped mill galvanized" or "mill galvanized."

Electrogalvanized (Suffix EGC)

Often referred to as "zinc plated" or "electroplated zinc," the steel and 0.5 mils of zinc are bonded by an electrolysis process. Electrogalvanizing is most commonly applied to small fittings, hardware, and threaded products.

GoldGalv® (No Suffix)

Gold colored zinc dichromate is applied over the zinc, producing a chemically bonded non porous barrier for protection from moisture and air. This extends the protective life of the zinc, and provides an excellent base for paint, if desired. The GoldGalv® hardware finish also provides a low electrical resistance when grounding of the system is required. Superstrut® channel and fittings are plated after fabrication, so there are no unprotected edges from cutting or punching. Where field cutting is necessary or scratches occur due to construction handling, you still have the sacrificial protection of the plated zinc to minimize the corrosion of raw edges and prevent spreading.

Hot-Dipped Galvanized (Suffix HDGC)

The material is zinc coated after fabrication providing total product protection on all surfaces. The fabricated channel or fitting is suspended and then dipped into tanks of hot zinc for a prolonged period, creating a coherent bond. The result is superior corrosion resistance as compared to pregalvanized material. Hot-dipped galvanizing is not recommended for threaded products, considering the zinc coating thickness will often disrupt the threads. Superstrut® hot-dipped galvanized is in conformance with ASTM Specifications A-123 (formerly A-386) and A-153. Superstrut channels maintain a minimum 1.5 oz. of zinc per square foot of steel or 2.5 mils (ASTM A-123, Thickness Grade 65). This finish is also referred to as "Hot-dipped galvanized after fabrication."

SPECIAL MATERIALS

Aluminum (Suffix ALC)

Superstrut® channel is available in aluminum. Fittings in HDG finish or fiberglass material are suggested for fastening products.

Stainless Steel

Superstrut® channel is supplied in Type 304 (SS) and Type 316 (T316L) stainless steel. All fittings and accessories are in 316SS (SS6). Contact your Regional Sales Office for availability.

Thomas & Betts reserves the right to change material and finish specifications without notice, to improve its products.



Epoxy Powder Coated — Green, Gray or White (Suffix GR, GY or WH)

Epoxy powder resins are applied electrostatically to the steel after fabrication. Once the material is completely covered with the powder-form epoxy, it proceeds through a 400°F (204°C) baking process for ten minutes, creating a chemical bond. This results in a minimum of 1.5 mil thickness of epoxy coating providing excellent resistance to chipping or peeling.



SECTION 1 **CHANNELS AND CONCRETE INSERTS**

Thomas&Betts

Channels and Concrete Inserts**CHANNEL****Material**

Steel channels are cold-roll formed from strip steel. Aluminum and Fiberglass channels are extruded profiles.

Material Thickness

All series 1200 12 gauge material

All series 1400 14 gauge material

All series 1600 16 gauge ribbed material

Standard Lengths

Standard lengths for channel are 10 ft and 20 ft with a tolerance of +1/8". Special lengths can be requested; however, minimum quantities may apply. Channels are sold per foot.

Warning

Load tables, charts, and design criteria provided in this catalogue are intended as guides only. Selection of proper product, support spacing, erection, and placement are the responsibility of the user.

When improperly used as tools of erection pipe hanger products have occasionally failed. To avoid an accident, the user is cautioned to use the product only as it was intended.

CONCRETE INSERT**Material**

Superstrut continuous insert channel is manufactured from 12 gauge hot rolled strip steel in two basic sizes as follows:

Cat. No. A302

1-5/8" x 1-5/8" 7/8" slot

Cat. No. C302

1-5/8" x 1-3/8" 7/8" slot

Cat. No. C302

1-5/8" x 1-3/8" 7/8" slot

Standard Lengths

Standard lengths are 10 ft and 20 ft. Product is supplied with foam filler and end caps to prevent concrete from seeping into channel.

Application


For casting into concrete walls, floors or ceilings to provide for attachment anywhere along the continuous slot.

Design Data

Load ratings as shown have a safety factor of 3 in 3000 lb. hard rock concrete. Where sound concrete does not exist, the load ratings shall not apply.

GoldGalv[®] hardware finish is standard for all Superstrut Concrete insert products. This is a multi-process finish of electro-plated zinc, followed by gold colored zinc dichromate to give excellent corrosion resistance and a superior paint base.

For more information on load design, see Section 8 for Engineering Data and Specifications.



Channels and Concrete Inserts






Channel Selection Chart

CHANNEL	HOLE CONFIGURATIONS					LENGTH	FINISH ON STEEL					MATÉRIAUX SPÉCIAUX				
Series	HS	S	SW	P	KO	ft	BC	PG(C)	EG(C)	GoldGalv®	HDG(C)	GR,GY,WH	PV(C)	AL(C)	T316L	SS6(C)
A1200						10 or 20										
A1400						10 or 20										
AR1600						10 or 20										
B1200						10 or 20										
B1400						10 or 20										
BR1600						10 or 20										
C1200						10 or 20										
D1200						10 or 20										
E1200						10 or 20										
H1200						10 or 20										

Legend

EXAMPLES	HOLE CONFIGURATION	FINISH ON STEEL	SPECIAL MATERIALS
A120010PG	Suffix	Suffix	Suffix
blank	Plain, no holes	BC	AL
HS	Half slot	PGC	Aluminum
S	Slotted	EGC	SS6 (C) Stainless Steel Type 316
SW	Slotted wide	No Suffix	T316L Stainless Steel Type 316L
P	Punched	HDGC	SS (C) Stainless Steel Type 304 *
KO	Knockout	GR,GY,WH	GoldGalv®
E1200HS20HDG	Standard offering.	Hot dipped galvanized	Epoxy paint in green (GR), grey (GY), or white (WH)
			*Check with your Regional Sales Office

Hole Configuration




KO: 1/16"


Holes: 9/16"

Slots: 9/16"


Slots: 9/16" X 3"

SECTION 1**Channels and Concrete Inserts****Welded Combinations**


02



02A




02B




02C


EXAMPLES
Two A1200 channels back to back are ordered as A1202. Two A1200 channels back to side are ordered as A1202C.




03A




03B




03C



03D




03E




04

Back to back steel channel is riveted at every 4 inches. Aluminum back to back channel are extruded profiles. All other combinations are spot welded at every 4 inches.

End Caps and Closure Strips**A804****End Cap**

Cat. No.	For Channel	Wt./C lb
A804EG	A1200	10
	A1400 AR1600	10
B804EG	B1400 BR1600	5
C804EG	C1200	8
E804EG	E1200	15
H804	H1200	20

Safety End Cap


Cat. No.	For Channel	Wt/C lb
A804NEOPWH	A1200 AR1600	1.75
	A1400	
B804NEOPWH	B1200-BR1600	1.5
H804NEOPWH	H1200	2

1-5/8" x 1-5/8" White Plastisol.

A2431**End Cap**

For A1200 Channel
Available in GoldGalv® or
Electrogalvanized (EG).


Wt./C 16 lb

A208


A208HDGC
A208EG
A208
A208SS6C

Does not include
stud nut or bolts.

For A and AR
series channel.
Wt./C 275 lb

A213**Inside Joiner**

For A1200 Series only.
Available only in GoldGalv® finish.








AB844PGC
Pre-Galvanized Closure Strip
AB844PCGY
Plastic Closure Strip
Colour: Grey

For all channel. Standard lengths 10 ft

AB844PC
Plastic Closure Strip
Colour: Gold


Channels and Concrete Inserts**Concrete Inserts**

<p>Concrete Channel Inserts</p> <p>*Finishes HDGC GoldGalv® PGC</p>  <p>Insert with end caps and foam closure strip installed.</p> <table border="1" data-bbox="160 783 586 939"> <thead> <tr> <th>Cat. No.</th><th>Length</th><th>Gauge</th><th>Wt.</th></tr> </thead> <tbody> <tr> <td>A302-10*</td><td>10 ft</td><td>12</td><td>2.19 lb/ft</td></tr> <tr> <td>A302-20*</td><td>20 ft</td><td>12</td><td>2.19 lb/ft</td></tr> <tr> <td>B302-10*</td><td>10 ft</td><td>12</td><td>1.36 lb/ft</td></tr> <tr> <td>B302-20*</td><td>20 ft</td><td>12</td><td>1.36 lb/ft</td></tr> <tr> <td>C302-10*</td><td>10 ft</td><td>12</td><td>1.81 lb/ft</td></tr> </tbody> </table> <p>Design Load 2000 lb per foot in hard rock concrete with a safety factor of 3. Standard lengths 10 ft and 20 ft. Length tolerance: 3/16 in.</p>	Cat. No.	Length	Gauge	Wt.	A302-10*	10 ft	12	2.19 lb/ft	A302-20*	20 ft	12	2.19 lb/ft	B302-10*	10 ft	12	1.36 lb/ft	B302-20*	20 ft	12	1.36 lb/ft	C302-10*	10 ft	12	1.81 lb/ft	<p>Anchor Caps</p> <p>*Finishes EGC GoldGalv®</p>  <p>12 gauge, Wt./C: 30 lb/C</p> <p>A450* For A Series C450* For C Series</p> <p>From pieces of A, B, C channel and a pair of anchor caps, short concrete inserts can be fabricated in the field.</p>	<p>460-10TB Removable Plastic Closure Strip</p>  <p>Designed as an added precaution to keep insert free of concrete. Closure strip fits all 1-5/8" wide strip inserts, regardless of depth.</p> <p>Order per 10 foot, standard length is 10 ft Material - Black Plastic Wt./C 52 lb</p>
Cat. No.	Length	Gauge	Wt.																							
A302-10*	10 ft	12	2.19 lb/ft																							
A302-20*	20 ft	12	2.19 lb/ft																							
B302-10*	10 ft	12	1.36 lb/ft																							
B302-20*	20 ft	12	1.36 lb/ft																							
C302-10*	10 ft	12	1.81 lb/ft																							
<p>SI400 Spot Insert Kit</p> <p>STD PACK: 10</p>  <table border="1" data-bbox="160 1639 603 1764"> <thead> <tr> <th>Cat. No.</th><th>Length ft.</th><th>O.D. Insert</th><th>Wt./C lb</th></tr> </thead> <tbody> <tr> <td>SI400-3/8</td><td>3/8x13x2-3/4</td><td>2x5/8</td><td>10</td></tr> <tr> <td>SI400-1/2</td><td>1/2x13x1-1/4</td><td>2-1/2x7/8</td><td>35</td></tr> </tbody> </table> <p>Other sizes available Maximum recommended load: SI400-3/8 = 450 lb/204 kg SI400-1/2 = 1000 lb/454 kg</p>	Cat. No.	Length ft.	O.D. Insert	Wt./C lb	SI400-3/8	3/8x13x2-3/4	2x5/8	10	SI400-1/2	1/2x13x1-1/4	2-1/2x7/8	35	<p>452TB Spot Insert</p>  <p>Standard Finish – GoldGalv®</p> <p>An insert with a knockout saves covering the opening. Accommodates hanger rod sizes from 1/4" through 7/8" by means of an AB102 insert nut, to be ordered separately.</p> <p>Design load: 1350 lb in 3000 lb. hard rock concrete with a safety factor of 3.</p> <p>Complies with Specification MSS SP69, Type 18.</p>	<p>Wt./C 52 lb</p>												
Cat. No.	Length ft.	O.D. Insert	Wt./C lb																							
SI400-3/8	3/8x13x2-3/4	2x5/8	10																							
SI400-1/2	1/2x13x1-1/4	2-1/2x7/8	35																							



SECTION 2
THREADED PRODUCTS AND HARDWARE

Thomas&Betts



CHANNEL NUTS

Superstrut® channel nuts are manufactured from Grade 2 mild steel and are case hardened.

Design Data

Superstrut® self aligning channel nuts are designed to provide resistance to pullout and resistance to side slip in excess of the full strength of the channels with which they are used. The extreme resistance to side slip results from the unique design of the alternate teeth, spaced and designed to develop a wedging action that increases with pressure or load.

Screw Threads

All threaded products are American Standard thread, free fit class 2.

Thread Size	1/4	5/16	3/8	1/2	5/8	3/4	7/8	1
Threads per inch	20	18	16	13	11	10	9	8
Design Torque (ft-lb)	6	11	19	50	100	125	185	275

Finish and special materials









Standard finish for all hardware is Electrogalvanized (EGC), GoldGalv®. Stainless Steel Type 316 is also available. Contact your Regional Sales Office for availability and minimum quantities.

Spring Nut Selector Chart




SPRING NUT	CHANNEL SERIES						
	A - AR	B - BR	C	D	E	F	H
A100-1/4EGC							
A100-5/16EGC							
A100-3/8EGC							
A100-1/2EGC							
A100-3/4							
B100-1/4EGC							
B100-5/16EGC							
B100-3/8EGC							
B100-1/2EGC							
H100-3/8EGC							
H100-1/2EGC							
CM100-1/4							
CM100-3/8							
CM100-1/2							
CM100-1/2B							
UC100-1/4							
UC100-3/8							
UC100-1/2							

SECTION 2

Threaded Products and Hardware

<p>A100 Regular Spring Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>A100-1/4EGC</td><td>1/4</td><td>8</td></tr> <tr><td>A100-5/16EGC</td><td>5/16</td><td>9</td></tr> <tr><td>A100-3/8EGC</td><td>3/8</td><td>10</td></tr> <tr><td>A100-1/2EGC</td><td>1/2</td><td>12</td></tr> <tr><td colspan="3">Nut is square over 1/2" size.</td></tr> <tr><td>A100-5/8EGC</td><td>5/8</td><td>19</td></tr> <tr><td>A100-3/4</td><td>3/4</td><td>19</td></tr> <tr><td>A100-7/8</td><td>7/8</td><td>18</td></tr> </tbody> </table> <p>Available in Stainless Steel 316. For all A and C series channel and inserts.</p>	Cat. No.	Size	Wt./C lb	A100-1/4EGC	1/4	8	A100-5/16EGC	5/16	9	A100-3/8EGC	3/8	10	A100-1/2EGC	1/2	12	Nut is square over 1/2" size.			A100-5/8EGC	5/8	19	A100-3/4	3/4	19	A100-7/8	7/8	18	<p>B100 Short Spring Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>B100-1/4EGC</td><td>1/4</td><td>7</td></tr> <tr><td>B100-5/16EGC</td><td>5/16</td><td>8</td></tr> <tr><td>B100-3/8EGC</td><td>3/8</td><td>9</td></tr> <tr><td>B100-1/2EGC</td><td>1/2</td><td>9</td></tr> </tbody> </table> <p>For all B and D series channel and inserts.</p>	Cat. No.	Size	Wt./C lb	B100-1/4EGC	1/4	7	B100-5/16EGC	5/16	8	B100-3/8EGC	3/8	9	B100-1/2EGC	1/2	9	<p>H100 Long Spring Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>H100-3/8EGC</td><td>3/8</td><td>10</td></tr> <tr><td>H100-1/2EGC</td><td>1/2</td><td>14</td></tr> </tbody> </table> <p>For all E and H series channel and inserts.</p>	Cat. No.	Size	Wt./C lb	H100-3/8EGC	3/8	10	H100-1/2EGC	1/2	14			
Cat. No.	Size	Wt./C lb																																																						
A100-1/4EGC	1/4	8																																																						
A100-5/16EGC	5/16	9																																																						
A100-3/8EGC	3/8	10																																																						
A100-1/2EGC	1/2	12																																																						
Nut is square over 1/2" size.																																																								
A100-5/8EGC	5/8	19																																																						
A100-3/4	3/4	19																																																						
A100-7/8	7/8	18																																																						
Cat. No.	Size	Wt./C lb																																																						
B100-1/4EGC	1/4	7																																																						
B100-5/16EGC	5/16	8																																																						
B100-3/8EGC	3/8	9																																																						
B100-1/2EGC	1/2	9																																																						
Cat. No.	Size	Wt./C lb																																																						
H100-3/8EGC	3/8	10																																																						
H100-1/2EGC	1/2	14																																																						
<p>AB100 Springless Nut 1/4" thick</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>AB100-1/4EGC</td><td>1/4</td><td>7</td></tr> <tr><td>AB100-5/16EGC</td><td>5/16</td><td>8</td></tr> <tr><td>AB100-3/8EGC</td><td>3/8</td><td>9</td></tr> <tr><td>AB100-1/2EGC</td><td>1/2</td><td>9</td></tr> </tbody> </table> <p>Nut is square over 1/2" size</p> <p>AB100-5/8EGC 5/8 10 AB100-3/4EG 3/4 10</p> <p>For use with all channels.</p>	Cat. No.	Size	Wt./C lb	AB100-1/4EGC	1/4	7	AB100-5/16EGC	5/16	8	AB100-3/8EGC	3/8	9	AB100-1/2EGC	1/2	9	<p>AC100 Springless Nut Heavy duty 3/8" thick</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>AC100-1/4EGC</td><td>1/4</td><td>7</td></tr> <tr><td>AC100-3/8EGC</td><td>3/8</td><td>9</td></tr> <tr><td>AC100-1/2EGC</td><td>1/2</td><td>11</td></tr> </tbody> </table> <p>Nut is square over 1/2" size</p> <p>AC100-5/8EGC 5/8 18 AC100-3/4EGC 3/4 18</p> <p>For all A, C, E and H series channel and inserts.</p>	Cat. No.	Size	Wt./C lb	AC100-1/4EGC	1/4	7	AC100-3/8EGC	3/8	9	AC100-1/2EGC	1/2	11	<p>813EG Springless Nut Light Duty</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>813EG</td><td>1/4</td><td>5</td></tr> </tbody> </table> <p>For use with all channels.</p>	Cat. No.	Size	Wt./C lb	813EG	1/4	5																					
Cat. No.	Size	Wt./C lb																																																						
AB100-1/4EGC	1/4	7																																																						
AB100-5/16EGC	5/16	8																																																						
AB100-3/8EGC	3/8	9																																																						
AB100-1/2EGC	1/2	9																																																						
Cat. No.	Size	Wt./C lb																																																						
AC100-1/4EGC	1/4	7																																																						
AC100-3/8EGC	3/8	9																																																						
AC100-1/2EGC	1/2	11																																																						
Cat. No.	Size	Wt./C lb																																																						
813EG	1/4	5																																																						
<p>A182 to A185 Regular Spring Stud Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Bolt Dia.</th> <th>Length A</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>A182-1/4x100EG</td><td>1/4</td><td>1</td><td>10</td></tr> <tr><td>A182-1/4x125EG</td><td>1/4</td><td>1-1/4</td><td>15</td></tr> <tr><td>A184-3/8x100EG</td><td>3/8</td><td>1</td><td>10</td></tr> <tr><td>A184-3/8x125EG</td><td>3/8</td><td>1-1/4</td><td>15</td></tr> <tr><td>A185-1/2x100EG</td><td>1/2</td><td>1</td><td>10</td></tr> <tr><td>A185-1/2x125EG</td><td>1/2</td><td>1-1/4</td><td>15</td></tr> </tbody> </table> <p>For all A and C series channels.</p>	Cat. No.	Bolt Dia.	Length A	Wt./C lb	A182-1/4x100EG	1/4	1	10	A182-1/4x125EG	1/4	1-1/4	15	A184-3/8x100EG	3/8	1	10	A184-3/8x125EG	3/8	1-1/4	15	A185-1/2x100EG	1/2	1	10	A185-1/2x125EG	1/2	1-1/4	15	<p>A177 to A180 Springless Stud Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Bolt Dia.</th> <th>Length A</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>A177-1/4x100EG</td><td>1/4</td><td>1</td><td>8</td></tr> <tr><td>A177-1/4x125EG</td><td>1/4</td><td>1-1/4</td><td>10</td></tr> <tr><td>A179-3/8x100EG</td><td>3/8</td><td>1</td><td>13</td></tr> <tr><td>A179-3/8x125EG</td><td>3/8</td><td>1-1/4</td><td>13.5</td></tr> </tbody> </table> <p>For use with all channels.</p>	Cat. No.	Bolt Dia.	Length A	Wt./C lb	A177-1/4x100EG	1/4	1	8	A177-1/4x125EG	1/4	1-1/4	10	A179-3/8x100EG	3/8	1	13	A179-3/8x125EG	3/8	1-1/4	13.5	<p>812 Stud Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>For Channel</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>812-1EG</td><td>1/4 x 1</td><td>6</td></tr> </tbody> </table> <p>For attaching fixture to channel slot down or to channel slot up knockouts. Specify length. Hex nut included.</p>	Cat. No.	For Channel	Wt./C lb	812-1EG	1/4 x 1	6
Cat. No.	Bolt Dia.	Length A	Wt./C lb																																																					
A182-1/4x100EG	1/4	1	10																																																					
A182-1/4x125EG	1/4	1-1/4	15																																																					
A184-3/8x100EG	3/8	1	10																																																					
A184-3/8x125EG	3/8	1-1/4	15																																																					
A185-1/2x100EG	1/2	1	10																																																					
A185-1/2x125EG	1/2	1-1/4	15																																																					
Cat. No.	Bolt Dia.	Length A	Wt./C lb																																																					
A177-1/4x100EG	1/4	1	8																																																					
A177-1/4x125EG	1/4	1-1/4	10																																																					
A179-3/8x100EG	3/8	1	13																																																					
A179-3/8x125EG	3/8	1-1/4	13.5																																																					
Cat. No.	For Channel	Wt./C lb																																																						
812-1EG	1/4 x 1	6																																																						
<p>CM100 Nylon Cone Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>CM100-1/4</td><td>1/4</td><td>8</td></tr> <tr><td>CM100-3/8</td><td>3/8</td><td>10</td></tr> <tr><td>* CM100-1/2</td><td>1/2</td><td>12</td></tr> <tr><td>** CM100B-1/2</td><td>1/2</td><td>10</td></tr> </tbody> </table> <p>GoldGalv® only For all 1-5/8" channel *Will not fit B Series channel **For B Series channel</p>	Cat. No.	Size	Wt./C lb	CM100-1/4	1/4	8	CM100-3/8	3/8	10	* CM100-1/2	1/2	12	** CM100B-1/2	1/2	10	<p>UC100 Universal Nylon Cone Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>UC100-1/4</td><td>1/4</td><td>8</td></tr> <tr><td>UC100-3/8</td><td>3/8</td><td>10</td></tr> <tr><td>UC100-1/2</td><td>1/2</td><td>12</td></tr> </tbody> </table> <p>GoldGalv® only For all 1-5/8" and 1-1/2" channels May be used with ALL Strut Depths. Can be used for CM100 Series, A100 Series, B100 Series and AB100 Series.</p>	Cat. No.	Size	Wt./C lb	UC100-1/4	1/4	8	UC100-3/8	3/8	10	UC100-1/2	1/2	12	<p>AB102 Unhardened Square Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>AB102-1/4</td><td>1/4</td><td>13</td></tr> <tr><td>AB102-3/8</td><td>3/8</td><td>14</td></tr> <tr><td>AB102-1/2</td><td>1/2</td><td>14</td></tr> <tr><td>AB102-5/8</td><td>5/8</td><td>12</td></tr> <tr><td>AB102-3/4</td><td>3/4</td><td>11</td></tr> <tr><td>AB102-7/8</td><td>7/8</td><td>10</td></tr> </tbody> </table>	Cat. No.	Size	Wt./C lb	AB102-1/4	1/4	13	AB102-3/8	3/8	14	AB102-1/2	1/2	14	AB102-5/8	5/8	12	AB102-3/4	3/4	11	AB102-7/8	7/8	10						
Cat. No.	Size	Wt./C lb																																																						
CM100-1/4	1/4	8																																																						
CM100-3/8	3/8	10																																																						
* CM100-1/2	1/2	12																																																						
** CM100B-1/2	1/2	10																																																						
Cat. No.	Size	Wt./C lb																																																						
UC100-1/4	1/4	8																																																						
UC100-3/8	3/8	10																																																						
UC100-1/2	1/2	12																																																						
Cat. No.	Size	Wt./C lb																																																						
AB102-1/4	1/4	13																																																						
AB102-3/8	3/8	14																																																						
AB102-1/2	1/2	14																																																						
AB102-5/8	5/8	12																																																						
AB102-3/4	3/4	11																																																						
AB102-7/8	7/8	10																																																						
<p>E145 Standard Hex Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E145-1/4EGC</td><td>1/4</td><td>.72</td></tr> <tr><td>E145-3/8EGC</td><td>3/8</td><td>1.60</td></tr> <tr><td>E145-1/2EGC</td><td>1/2</td><td>2.78</td></tr> <tr><td>E145-5/8EGC</td><td>5/8</td><td>6.92</td></tr> <tr><td>E145-3/4EGC</td><td>3/4</td><td>12.70</td></tr> <tr><td>E145-7/8EGC</td><td>7/8</td><td>19.00</td></tr> <tr><td>E145-1EGC</td><td>1</td><td>28.00</td></tr> </tbody> </table>	Cat. No.	Size	Wt./C lb	E145-1/4EGC	1/4	.72	E145-3/8EGC	3/8	1.60	E145-1/2EGC	1/2	2.78	E145-5/8EGC	5/8	6.92	E145-3/4EGC	3/4	12.70	E145-7/8EGC	7/8	19.00	E145-1EGC	1	28.00	<p>ES145 Swivel Nut and Jam Nut Combinations</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>ES145-3/8</td><td>3/8</td><td>5.5</td></tr> <tr><td>ES145-1/2</td><td>1/2</td><td>6.0</td></tr> </tbody> </table>	Cat. No.	Size	Wt./C lb	ES145-3/8	3/8	5.5	ES145-1/2	1/2	6.0	<p>E146 Standard Square Nut</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E146-1/4HDGC</td><td>1/4</td><td>.93</td></tr> <tr><td>E146-5/16HDGC</td><td>5/16</td><td>1.60</td></tr> <tr><td>E146-3/8HDGC</td><td>3/8</td><td>2.65</td></tr> <tr><td>E146-5/8HDGC</td><td>5/8</td><td>10.80</td></tr> </tbody> </table>	Cat. No.	Size	Wt./C lb	E146-1/4HDGC	1/4	.93	E146-5/16HDGC	5/16	1.60	E146-3/8HDGC	3/8	2.65	E146-5/8HDGC	5/8	10.80						
Cat. No.	Size	Wt./C lb																																																						
E145-1/4EGC	1/4	.72																																																						
E145-3/8EGC	3/8	1.60																																																						
E145-1/2EGC	1/2	2.78																																																						
E145-5/8EGC	5/8	6.92																																																						
E145-3/4EGC	3/4	12.70																																																						
E145-7/8EGC	7/8	19.00																																																						
E145-1EGC	1	28.00																																																						
Cat. No.	Size	Wt./C lb																																																						
ES145-3/8	3/8	5.5																																																						
ES145-1/2	1/2	6.0																																																						
Cat. No.	Size	Wt./C lb																																																						
E146-1/4HDGC	1/4	.93																																																						
E146-5/16HDGC	5/16	1.60																																																						
E146-3/8HDGC	3/8	2.65																																																						
E146-5/8HDGC	5/8	10.80																																																						

Threaded Products and Hardware

<p>E147 Flat Steel Washer</p>  <p>STD PACK: 100</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E147-1/4EG</td><td>1/4</td><td>.67</td></tr> <tr><td>E147-5/16EG</td><td>5/16</td><td>1.11</td></tr> <tr><td>E147-3/8EG</td><td>3/8</td><td>1.49</td></tr> <tr><td>E147-1/2EG</td><td>1/2</td><td>3.85</td></tr> <tr><td>E147-5/8EG</td><td>5/8</td><td>7.69</td></tr> <tr><td>E147-3/4EG</td><td>3/4</td><td>9.89</td></tr> <tr><td>E147-7/8EG</td><td>7/8</td><td>15.40</td></tr> </tbody> </table> <p>Available in Stainless Steel.</p>	Cat. No.	Size	Wt./C lb	E147-1/4EG	1/4	.67	E147-5/16EG	5/16	1.11	E147-3/8EG	3/8	1.49	E147-1/2EG	1/2	3.85	E147-5/8EG	5/8	7.69	E147-3/4EG	3/4	9.89	E147-7/8EG	7/8	15.40	<p>EF147 Fender Washer</p>  <p>STD PACK: 100</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>A</th> <th>B</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>EF147-1/4EGC</td><td>1/4</td><td>1-1/4</td><td>5/16</td><td>3.1</td></tr> <tr><td>EF147-3/8EGC</td><td>3/8</td><td>1-1/2</td><td>7/16</td><td>2.9</td></tr> <tr><td></td><td></td><td>1/2</td><td>2</td><td>9/16 5.0</td></tr> </tbody> </table> <p>Available in Stainless Steel.</p>	Cat. No.	Size	A	B	Wt./C lb	EF147-1/4EGC	1/4	1-1/4	5/16	3.1	EF147-3/8EGC	3/8	1-1/2	7/16	2.9			1/2	2	9/16 5.0	<p>E148 Lock Washer</p>  <p>STD PACK: 100</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E148-1/4EG</td><td>1/4</td><td>.26</td></tr> <tr><td>E148-3/8EG</td><td>3/8</td><td>.50</td></tr> <tr><td>E148-1/2EG</td><td>1/2</td><td>1.09</td></tr> <tr><td>E148-5/8EG</td><td>5/8</td><td>2.57</td></tr> </tbody> </table> <p>Available in Stainless Steel.</p>	Cat. No.	Size	Wt./C lb	E148-1/4EG	1/4	.26	E148-3/8EG	3/8	.50	E148-1/2EG	1/2	1.09	E148-5/8EG	5/8	2.57																																																		
Cat. No.	Size	Wt./C lb																																																																																																													
E147-1/4EG	1/4	.67																																																																																																													
E147-5/16EG	5/16	1.11																																																																																																													
E147-3/8EG	3/8	1.49																																																																																																													
E147-1/2EG	1/2	3.85																																																																																																													
E147-5/8EG	5/8	7.69																																																																																																													
E147-3/4EG	3/4	9.89																																																																																																													
E147-7/8EG	7/8	15.40																																																																																																													
Cat. No.	Size	A	B	Wt./C lb																																																																																																											
EF147-1/4EGC	1/4	1-1/4	5/16	3.1																																																																																																											
EF147-3/8EGC	3/8	1-1/2	7/16	2.9																																																																																																											
		1/2	2	9/16 5.0																																																																																																											
Cat. No.	Size	Wt./C lb																																																																																																													
E148-1/4EG	1/4	.26																																																																																																													
E148-3/8EG	3/8	.50																																																																																																													
E148-1/2EG	1/2	1.09																																																																																																													
E148-5/8EG	5/8	2.57																																																																																																													
<p>E142 Hex Head Cap Screw</p>  <p>STD PACK: 100</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E142-1/4x100EG</td><td>1/4x1</td><td>1.74</td></tr> <tr><td>E142-1/4x150EG</td><td>1/4x1-1/2</td><td>2.43</td></tr> <tr><td>E142-3/8x100EG</td><td>3/8x1</td><td>4.17</td></tr> <tr><td>E142-3/8x150EG</td><td>3/8x1-1/2</td><td>5.64</td></tr> <tr><td>E142-1/2x100EG</td><td>1/2x1</td><td>8.94</td></tr> <tr><td>E142-1/2x150EG</td><td>1/2x1-1/2</td><td>10.00</td></tr> <tr><td>E142-1/2x200EG</td><td>1/2x2</td><td>11.19</td></tr> <tr><td>E142-1/2x225EG</td><td>1/2x2-1/4</td><td>11.90</td></tr> <tr><td>E142-1/2x250EG</td><td>1/2x2-1/2</td><td>12.52</td></tr> <tr><td>E142-1/2x275EG</td><td>1/2x2-3/4</td><td>13.22</td></tr> </tbody> </table> <p>Available in Stainless Steel.</p>	Cat. No.	Size	Wt./C lb	E142-1/4x100EG	1/4x1	1.74	E142-1/4x150EG	1/4x1-1/2	2.43	E142-3/8x100EG	3/8x1	4.17	E142-3/8x150EG	3/8x1-1/2	5.64	E142-1/2x100EG	1/2x1	8.94	E142-1/2x150EG	1/2x1-1/2	10.00	E142-1/2x200EG	1/2x2	11.19	E142-1/2x225EG	1/2x2-1/4	11.90	E142-1/2x250EG	1/2x2-1/2	12.52	E142-1/2x275EG	1/2x2-3/4	13.22	<p>E150S Lag Bolt</p>  <p>STD PACK: 50</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Drill Size</th> <th>Size</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E150S-3/8x1-1/2EG</td><td>1/4</td><td>3/8x1-1/2</td><td>5</td></tr> <tr><td>E150S-3/8x2EG</td><td>1/4</td><td>3/8x2</td><td>7</td></tr> <tr><td>E150S-3/8x2-1/2EG</td><td>1/4</td><td>3/8x2-1/2</td><td>8</td></tr> <tr><td>E150S-3/8x3EG</td><td>1/4</td><td>3/8x3</td><td>9</td></tr> <tr><td>E150S-1/2x1-1/2EG</td><td>11/32</td><td>1/2x1-1/2</td><td>12</td></tr> <tr><td>E150S-1/2x2EG</td><td>11/32</td><td>1/2x2</td><td>13</td></tr> <tr><td>E150S-1/2x2-1/2EG</td><td>11/32</td><td>1/2x2-1/2</td><td>15</td></tr> <tr><td>E150S-1/2x3EG</td><td>11/32</td><td>1/2x3</td><td>18</td></tr> </tbody> </table>	Cat. No.	Drill Size	Size	Wt./C lb	E150S-3/8x1-1/2EG	1/4	3/8x1-1/2	5	E150S-3/8x2EG	1/4	3/8x2	7	E150S-3/8x2-1/2EG	1/4	3/8x2-1/2	8	E150S-3/8x3EG	1/4	3/8x3	9	E150S-1/2x1-1/2EG	11/32	1/2x1-1/2	12	E150S-1/2x2EG	11/32	1/2x2	13	E150S-1/2x2-1/2EG	11/32	1/2x2-1/2	15	E150S-1/2x3EG	11/32	1/2x3	18	<p>E151 Coach Screw Rod</p>  <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>Rod Size in.</th> <th>Standard Rod Lengths in.</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>E151-3/8x4EG</td><td>3/8</td><td>4</td><td>9</td></tr> <tr><td>E151-3/8x6EG</td><td>3/8</td><td>6</td><td>14</td></tr> <tr><td>E151-3/8x8EG</td><td>3/8</td><td>8</td><td>22</td></tr> <tr><td>E151-3/8x10EG</td><td>3/8</td><td>10</td><td>29</td></tr> <tr><td>E151-3/8x12EG</td><td>3/8</td><td>12</td><td>35</td></tr> <tr><td>E151-1/2x4EG</td><td>1/2</td><td>4</td><td>17</td></tr> <tr><td>E151-1/2x6EG</td><td>1/2</td><td>6</td><td>22</td></tr> <tr><td>E151-1/2x8EG</td><td>1/2</td><td>8</td><td>40</td></tr> <tr><td>E151-1/2x10EG</td><td>1/2</td><td>10</td><td>51</td></tr> </tbody> </table> <p>Machine threaded opposite end, carbon steel.</p>	Cat. No.	Rod Size in.	Standard Rod Lengths in.	Wt./C lb	E151-3/8x4EG	3/8	4	9	E151-3/8x6EG	3/8	6	14	E151-3/8x8EG	3/8	8	22	E151-3/8x10EG	3/8	10	29	E151-3/8x12EG	3/8	12	35	E151-1/2x4EG	1/2	4	17	E151-1/2x6EG	1/2	6	22	E151-1/2x8EG	1/2	8	40	E151-1/2x10EG	1/2	10	51
Cat. No.	Size	Wt./C lb																																																																																																													
E142-1/4x100EG	1/4x1	1.74																																																																																																													
E142-1/4x150EG	1/4x1-1/2	2.43																																																																																																													
E142-3/8x100EG	3/8x1	4.17																																																																																																													
E142-3/8x150EG	3/8x1-1/2	5.64																																																																																																													
E142-1/2x100EG	1/2x1	8.94																																																																																																													
E142-1/2x150EG	1/2x1-1/2	10.00																																																																																																													
E142-1/2x200EG	1/2x2	11.19																																																																																																													
E142-1/2x225EG	1/2x2-1/4	11.90																																																																																																													
E142-1/2x250EG	1/2x2-1/2	12.52																																																																																																													
E142-1/2x275EG	1/2x2-3/4	13.22																																																																																																													
Cat. No.	Drill Size	Size	Wt./C lb																																																																																																												
E150S-3/8x1-1/2EG	1/4	3/8x1-1/2	5																																																																																																												
E150S-3/8x2EG	1/4	3/8x2	7																																																																																																												
E150S-3/8x2-1/2EG	1/4	3/8x2-1/2	8																																																																																																												
E150S-3/8x3EG	1/4	3/8x3	9																																																																																																												
E150S-1/2x1-1/2EG	11/32	1/2x1-1/2	12																																																																																																												
E150S-1/2x2EG	11/32	1/2x2	13																																																																																																												
E150S-1/2x2-1/2EG	11/32	1/2x2-1/2	15																																																																																																												
E150S-1/2x3EG	11/32	1/2x3	18																																																																																																												
Cat. No.	Rod Size in.	Standard Rod Lengths in.	Wt./C lb																																																																																																												
E151-3/8x4EG	3/8	4	9																																																																																																												
E151-3/8x6EG	3/8	6	14																																																																																																												
E151-3/8x8EG	3/8	8	22																																																																																																												
E151-3/8x10EG	3/8	10	29																																																																																																												
E151-3/8x12EG	3/8	12	35																																																																																																												
E151-1/2x4EG	1/2	4	17																																																																																																												
E151-1/2x6EG	1/2	6	22																																																																																																												
E151-1/2x8EG	1/2	8	40																																																																																																												
E151-1/2x10EG	1/2	10	51																																																																																																												
<p>H104 Hanger Rod Continuous Threaded</p>  <p>STD PACK: 3</p> <ul style="list-style-type: none"> Black available upon request. Sold per foot; standard length, 10 ft Also available in stainless steel (304 and 316) standard length 6 ft National coarse thread <table border="1"> <thead> <tr> <th rowspan="2">Cat. No.</th> <th rowspan="2">Thread Size</th> <th colspan="2">Design</th> </tr> <tr> <th>Wt./lb 100 ft</th> <th>Load lb</th> </tr> </thead> <tbody> <tr><td>H104-1/4x10EGC</td><td>1/4</td><td>12.5</td><td>150</td></tr> <tr><td>H104-3/8x10EGC</td><td>3/8</td><td>29</td><td>610</td></tr> <tr><td>H104-1/2x10EGC</td><td>1/2</td><td>53.5</td><td>1130</td></tr> <tr><td>H104-5/8x10EGC</td><td>5/8</td><td>85</td><td>1810</td></tr> <tr><td>H104-3/4x10EGC</td><td>3/4</td><td>123</td><td>2710</td></tr> <tr><td>H104-7/8x10EG</td><td>7/8</td><td>130</td><td>3770</td></tr> <tr><td>H104-1x10EG</td><td>1</td><td>214</td><td>4960</td></tr> </tbody> </table> <p>Available in 12' Stainless Steel.</p>	Cat. No.	Thread Size	Design		Wt./lb 100 ft	Load lb	H104-1/4x10EGC	1/4	12.5	150	H104-3/8x10EGC	3/8	29	610	H104-1/2x10EGC	1/2	53.5	1130	H104-5/8x10EGC	5/8	85	1810	H104-3/4x10EGC	3/4	123	2710	H104-7/8x10EG	7/8	130	3770	H104-1x10EG	1	214	4960	<p>H119 Rod Couplings</p>  <p>Standard Rod Coupling Example: H119-1/2EG</p> <table border="1"> <thead> <tr> <th>Rod Size</th> <th>A</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>1/4</td><td>7/8</td><td>1.90</td></tr> <tr><td>5/16</td><td>7/8</td><td>3.75</td></tr> <tr><td>3/8</td><td>1-1/8</td><td>3.50</td></tr> <tr><td>1/2</td><td>1-1/4</td><td>5.50</td></tr> <tr><td>5/8</td><td>2-1/8</td><td>18.00</td></tr> <tr><td>3/4</td><td>2-1/4</td><td>28.00</td></tr> <tr><td>7/8</td><td>2-1/2</td><td>55.00</td></tr> <tr><td>1</td><td>2-1/4</td><td>56.00</td></tr> </tbody> </table> <p>Rod Reducer Coupling Example: H119-1/4x3/8EG</p> <table border="1"> <thead> <tr> <th>Rod Size</th> <th>A</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>1/4 to 3/8</td><td>1-1/2</td><td>3.50</td></tr> <tr><td>3/8 to 1/2</td><td>1-1/4</td><td>6.70</td></tr> <tr><td>1/2 to 5/8</td><td>1-1/4</td><td>14.00</td></tr> <tr><td>5/8 to 3/4</td><td>1-1/2</td><td>21.00</td></tr> <tr><td>3/4 to 7/8</td><td>1-3/4</td><td>40.00</td></tr> </tbody> </table> <p>Order by product number, rod size, and finish. Available in Stainless Steel.</p>	Rod Size	A	Wt./C lb	1/4	7/8	1.90	5/16	7/8	3.75	3/8	1-1/8	3.50	1/2	1-1/4	5.50	5/8	2-1/8	18.00	3/4	2-1/4	28.00	7/8	2-1/2	55.00	1	2-1/4	56.00	Rod Size	A	Wt./C lb	1/4 to 3/8	1-1/2	3.50	3/8 to 1/2	1-1/4	6.70	1/2 to 5/8	1-1/4	14.00	5/8 to 3/4	1-1/2	21.00	3/4 to 7/8	1-3/4	40.00																															
Cat. No.			Thread Size	Design																																																																																																											
	Wt./lb 100 ft	Load lb																																																																																																													
H104-1/4x10EGC	1/4	12.5	150																																																																																																												
H104-3/8x10EGC	3/8	29	610																																																																																																												
H104-1/2x10EGC	1/2	53.5	1130																																																																																																												
H104-5/8x10EGC	5/8	85	1810																																																																																																												
H104-3/4x10EGC	3/4	123	2710																																																																																																												
H104-7/8x10EG	7/8	130	3770																																																																																																												
H104-1x10EG	1	214	4960																																																																																																												
Rod Size	A	Wt./C lb																																																																																																													
1/4	7/8	1.90																																																																																																													
5/16	7/8	3.75																																																																																																													
3/8	1-1/8	3.50																																																																																																													
1/2	1-1/4	5.50																																																																																																													
5/8	2-1/8	18.00																																																																																																													
3/4	2-1/4	28.00																																																																																																													
7/8	2-1/2	55.00																																																																																																													
1	2-1/4	56.00																																																																																																													
Rod Size	A	Wt./C lb																																																																																																													
1/4 to 3/8	1-1/2	3.50																																																																																																													
3/8 to 1/2	1-1/4	6.70																																																																																																													
1/2 to 5/8	1-1/4	14.00																																																																																																													
5/8 to 3/4	1-1/2	21.00																																																																																																													
3/4 to 7/8	1-3/4	40.00																																																																																																													

SECTION 2

Threaded Products and Hardware

H122

Trapnut™ Strut Fastener





Finishes

Electrogalvanized (EG)
GoldGalv®
Stainless Steel Type 316 (SS6)

Cat. No.	Size	Design Load lb	Std. Ctn.
H 122 1/4	1/4	150	50
H 122 3/8	3/8	590	50
H 122 1/2	1/2	1080	50
H 122 1/4 EG	1/4	150	50
H 122 3/8 EG	3/8	590	50
H 122 1/2 EG	1/2	1080	50
H 122 1/4 SS6	1/4	150	50
H 122 3/8 SS6	3/8	590	50
H 122 1/2 SS6	1/2	1080	50

M117

Eye Socket




Rod Size A	Pipe Size	B	E	Wt./C lb	Design Load, lb
1/4	3/8	1/4	1-11/32	5	230
3/8	1/2 - 2	1/4	1-11/32	7	610
1/2	2-1/2 - 3-1/2	1/4	1-17/32	13	1130
5/8	4 - 5	3/8	1-13/16	19	1810
3/4	6	1/2	2-5/32	31	2400
7/8	8	1/2	2-11/32	44	2800

Standard Finishes - Bare (B), Electrogalvanized (EG)

Malleable iron. For attaching hanger rod to various types of hangers and beam clamps
Order by product number, rod size, and finish. Example: M117-1/4B
Complies with Specification MSS SP69, Type 16.

E120

Swivel Joint



Cat. No.	Size	A	B	Design Load	
				Wt./C lb	lb
E120-3/8	3/8	1-3/8	3/8	15	1000
E120-1/2	1/2	1-1/2	1/2	25	1800


E120A

Weldless Eye Nut

Standard Finish - Bare (B)


Drop Forged Steel
For use on high temperature piping installations.
Order by product number and rod size.
Example: E120A-3/8B

Rod Size T	A	B	C	D	E	F	Design Load	
							Wt./C lb	lb
3/8	7/8	5/8	1-1/4	2	2-1/2	3/8	20	2700
1/2	7/8	5/8	1-1/4	2	2-1/2	3/8	22	2700
5/8	1-3/8	3/4	1-1/2	2-1/2	3	1/2	60	5000
3/4	1-3/8	3/4	1-1/2	2-1/2	3	1/2	56	5000
7/8	1-1/2	1-5/8	1-5/16	3-5/8	4-1/2	3/4	174	10000
1	1-1/2	1-5/8	1-5/16	3-5/8	4-1/2	3/4	168	10000



E122


Swivel Joint



Cat. No.	Size	A	B	Design Load	
				Wt./C lb	lb
E122-3/8	3/8	1-3/8	3/8	28	1000
E122-1/2	1/2	1-1/2	1/2	48	1800

E130


Swivel Joint



Cat. No.	Size	A	B	Design Load	
				Wt./C lb	lb
E130-3/8	3/8	1-3/8	3/8	23	1000
E130-1/2	1/2	1-1/2	1/2	28	1800

E131

Swivel Joint




Cat. No.	Size	A	B	Design Load	
				Wt./C lb	lb
E131-3/8	3/8	1-3/8	3/8	25	1000
E131-1/2	1/2	1-1/2	1/2	52	1800

Threaded Products and Hardware

C781
 Square Washer

*Finishes
B
HDG
EG
SS6


Cat. No.	Rod Size	Hole Size	Overall Dimensions	Wt./C lb
C781-3/8*	3/8	7/16	3 x 3 x 3/16	27
C781-1/2*	1/2	9/16	3 x 3 x 3/16	27
C781-5/8*	5/8	11/16	3 x 3 x 1/4	47
C781-3/4*	3/4	13/16	3 x 3 x 1/4	42
C781-7/8*	7/8	15/16	4 x 4 x 3/8	85
C781-1*	1	1-1/8	4 x 4 x 3/8	160



Used for beam applications.
For channel applications use AB241.

H115
 Standard U-Bolt

Pipe Size	A	B	C	D	E	Wt./C lb	Design Load lb
1/2	15/16	1-3/4	1-1/2	3/8	2-3/4	13	1500
3/4	1-1/8	1-3/4	1-5/8	3/8	3-1/16	15	2000
1	1-3/8	1-7/8	1-5/8	3/8	3-5/16	16	2500
1-1/4	1-23/32	1-3/4	1-15/32	3/8	3-1/2	17	2500
1-1/2	2	1-3/4	1-7/16	3/8	3-3/4	18	2500
2	2-7/16	2-1/16	1-7/8	3/8	4-11/16	32	3300
2-1/2	2-15/16	2-1/16	1-13/16	3/8	5-1/8	34	4000
3	3-9/16	2	1-3/4	3/8	5-11/16	38	4000
3-1/2	4-3/32	2	1-23/32	3/8	6-3/16	40	4000
4	4-19/32	2-1/4	1-31/32	1/2	6-15/16	46	4000
5	5-5/8	3	2-7/32	1/2	8-5/16	101	4000
6	6-3/4	3-3/4	2-13/16	5/8	10-1/8	197	4000
8	8-3/4	3-3/4	2-13/16	5/8	12-1/8	233	4000
10	10-7/8	4	3	3/4	14-9/16	491	5400
12	12-7/8	4-1/4	3-1/4	7/8	16-15/16	773	7500



Standard Finishes - Electrogalvanized (EG), GoldGalv®,
Stainless Steel or Bare (B)
Example: H115-1/2EG

Sizes through 4" furnished with one hex nut per leg.
Sizes 5" and above furnished with two hex nuts per leg.
Order by Cat. No., pipe size, finish.



Complies with Specification MSS SP69, Type 24.

For sizes 14 to 36", contact your Regional Sales Office.



SECTION 3 **FITTINGS AND BRACKETS**

Thomas&Betts

Fittings and Brackets**SECTION 3****Material**

Superstrut® fittings and brackets are manufactured from hot rolled carbon steel.

Dimensions

The following standard dimensions apply to all fittings except as indicated on the individual drawings.

Hole spacing 13/16" from end of fittings

Hole spacing 1-7/8" centers

Hole size 9/16" diameter

Material 1-5/8" wide

Material 1/4" thick

Application Instructions

Parts drawings illustrate a typical use for the fitting, and in many cases other uses for the part are appropriate.

Design Data

Load ratings vary depending fittings and brackets are used with 12, 14 or 16 gauge channel. Ratings are shown for each channel material. (See Section 8 Engineering Data and Specifications).

The material is zinc coated after fabrication providing total product protection on all surfaces. The fabricated channel or fitting is suspended and then dipped into tanks of hot zinc for a prolonged period, creating a coherent bond. Other finishes are available. Refer to page 4.

Nuts and Bolts Required

Unless otherwise noted, nuts and bolts for use with fittings and brackets should be ordered separately.

The standard bolt for the 9/16" hole is a 1/2" hex head cap screw 1" long. The 1" length may be used with all series channel.

Design Load

For more information on design load, see section 8 Engineering Data and Specifications.

Finishes and Special Materials

Standard finishes are Hot Dipped Galvanized (HDGC) and GoldGalv® (no suffix). Fittings are also available in Electrogalvanized (EG) and Stainless Steel 316 (SS6C). Contact your Regional Sales Office for availability and minimum quantities.
















Aluminum channel

For Aluminum channel, we suggest fittings in HDG(C) or SS6 (C).

SECTION 3

Fittings and Brackets

Flat Fittings

AB206  AB206HDGC AB206EG AB206 AB206SS6C Wt./C 35 lb	AB207  AB207HDGC AB207EG AB207 AB207SS6C Wt./C 52 lb	X207  X207HDG X207EG X207 X207SS6 Wt./C 78 lb
X208  X208HDG X208EG X208 X208SS6C Wt./C 88 lb	AB219  AB219HDGC AB219EG AB219 AB219SS6C Wt./C 53 lb	AB220  AB220HDGC AB220EG AB220 AB220SS6C Wt./C 78 lb
AB240  AB240HDG AB240EG AB240 Wt./C 69 lb	AB241  Cat. No. Bolt Size Wt./C lb AB241-1/4* 1/4 18 AB241-5/16* 5/16 18 AB241-3/8* 3/8 18 AB241-1/2* 1/2 17 AB241-5/8* 5/8 15 AB241-3/4* 3/4 14 *Finishes HDGC EG GoldGalv® SS6C	AB242  AB242HDGC AB242EG AB242 For use with either 3/8" or 1/2" hanger rod. Wt./C 9 lb
AB253  AB253HDGC AB253EG AB253 AB253SS6C Wt./C 97 lb	AB255  AB255HDGC AB255EG AB255 Wt./C 70 lb	AB257  AB257HDGC AB257EG AB257 Wt./C 105 lb
AB261  AB261HDGC AB261EG AB261 Wt./C 148 lb	AB263  AB263HDGC AB263EG AB263 AB263SS6 Wt./C 150 lb	AB265  AB265HDGC AB265EG AB265 Wt./C 105 lb

Standard Dimensions

Hole Spacing
Hole Spacing
Hole Size
Material
Material

13/16" From End
1-7/8" Centers
9/16" Diam.
1-5/8" Width
1/4" Thick

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)

Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

Fittings and Brackets

90° Fittings

AB201 AB201HDGC AB201EG AB201 AB201SS6C Wt./C 35 lb	AB202 AB202HDGC AB202EG AB202 AB202SS6C Wt./C 35 lb	AB203 AB203HDGC AB203EG AB203 AB203SS6C Wt./C 58 lb															
AB204 AB204HDGC AB204EG AB204 AB204SS6 Wt./C 58 lb	AB205 AB205HDGC AB205EG AB205 AB205SS6C Wt./C 78 lb	AB213 AB213HDGC AB213EG AB213 Wt./C 125 lb															
AB214 AB214HDGC AB214EG AB214 AB214SS6 Wt./C 125 lb	AB216 AB216HDGC AB216EG AB216SS6C Wt./C 135 lb	AB252 *Finishes HDGC GoldGalv® EG <table border="1"><thead><tr><th>Cat. No.</th><th>A</th><th>Wt./C</th></tr></thead><tbody><tr><td>AB252-1*</td><td>3-7/8</td><td>61</td></tr><tr><td>AB252-2*</td><td>5-7/8</td><td>84</td></tr><tr><td>AB252-3*</td><td>7-7/8</td><td>107</td></tr><tr><td>AB252-4*</td><td>9-7/8</td><td>130</td></tr></tbody></table>	Cat. No.	A	Wt./C	AB252-1*	3-7/8	61	AB252-2*	5-7/8	84	AB252-3*	7-7/8	107	AB252-4*	9-7/8	130
Cat. No.	A	Wt./C															
AB252-1*	3-7/8	61															
AB252-2*	5-7/8	84															
AB252-3*	7-7/8	107															
AB252-4*	9-7/8	130															
AB254R AB254RHDGC AB254REG AB254R Wt./C 105 lb	AB254L AB254LHDGC AB254LEG AB254L Wt./C 105 lb	AB260R AB260RHDGC AB260REG AB260R Wt./C 58 lb															
AB260L AB260LHDGC AB260LEG AB260L Wt./C 58 lb	AB274 AB274HDG AB274EG AB274 Wt./C 70 lb	AB275 AB275HDGC AB275EG AB275SS6C Wt./C 77 lb															

Standard Dimensions Hole Spacing 13/16" From End
 Hole Spacing 1-7/8" Centers
 Hole Size 9/16" Diam.
 Material 1-5/8" Width
 Material 1/4" Thick

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)

Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

Thomas & Betts





SECTION 3




Fittings and Brackets







90° Fittings

AB284R AB284RHDG AB284REG AB284R Wt./C 230 lb	AB284L AB284LHDG AB284LEG AB284L Wt./C 230 lb	AB299 AB299HDG AB299EG AB299 Wt./C 40 lb
X201 X201HDG X201EG X201 Wt./C 65 lb	X204 X204HDG X204EG X204 Wt./C 1-90 lb	X289 X289HDGC X289EG X289 Wt./C 105 lb
X299 X299HDGC X299EG X299 Wt./C 38 lb	N205 N205HDGC N205EG N205 N205SS6C Wt./C 74 lb	N219 N219HDG N219EG N219 N219SS6 Wt./C 71 lb

Fittings and Brackets**Angular Fittings**

AB225  Other angles available. Contact Customer Service. AB225HDGC AB225EG AB225 AB225SS6 Wt./C 58 lb	AB226  Other angles available. Contact Customer Service. AB226HDGC AB226SS6 Wt./C 119 lb	AB227  Other angles available. Contact Customer Service. AB227HDGC AB227EG AB227 AB227SS6 Wt./C 58 lb	AB228  Other angles available. Contact Customer Service. AB228HDGC AB228SS6C Wt./C 69 lb
--	---	---	--

AB231  AB231EG	AB232  AB232EG	AB239  *Finishes HDGC GoldGalv® EG <table border="1" style="margin-left: auto; margin-right: auto;"><thead><tr><th>Cat. No.</th><th>A</th><th>B</th><th>lb</th></tr></thead><tbody><tr><td>AB239-1*</td><td>7-13/16</td><td>8-1/2</td><td>148</td></tr><tr><td>AB239-2*</td><td>13-3/4</td><td>17</td><td>255</td></tr><tr><td>AB239-3*</td><td>19-3/4</td><td>25-1/2</td><td>363</td></tr></tbody></table>	Cat. No.	A	B	lb	AB239-1*	7-13/16	8-1/2	148	AB239-2*	13-3/4	17	255	AB239-3*	19-3/4	25-1/2	363
Cat. No.	A	B	lb															
AB239-1*	7-13/16	8-1/2	148															
AB239-2*	13-3/4	17	255															
AB239-3*	19-3/4	25-1/2	363															


"Z" Shape Fittings		
A209  For attaching A and AR series channel. A209HDGC A209EG A209 A209SS6 Wt./C 55 lb	B209  For attaching B and BR series channel. B209HDG B209EG B209 Wt./C 43 lb	C209  For attaching C series channel. C209 Wt./C 49 lb
D209  For attaching D series channel. D209HDG D209EG D209 Wt./C 45 lb	CZ209  For attaching H series and A back to back. CZ209EG CZ209 Wt./C 70 lb	EZ209  For attaching E series channel. EZ209HDGC EZ209EG EZ209 EZ209SS6 Wt./C 70 lb
Standard Dimensions Hole Spacing Hole Spacing Hole Size Material Material	Materials HDG(C) EG(C) (No suffix) SS6(C)	Hot-Dipped Galvanized Electrogalvanized GoldGalv® Stainless Steel 316

SECTION 3

Fittings and Brackets

"U" Shape Fittings

A208




Does not include stud nut or bolts.

A208HDGC
A208EG
A208
A208SS6C

For A and AR series channel.
Wt./C 275 lb


A213

Inside Joiner



For A1200 series
Available only in GoldGalv® finish
Wt./C 40 lb


A210



For attaching A and AR series channel.
Wt./C 88 lb


A210HDGC
A210EG
A210
A210SS6C

A211



For attaching A and AR series double channel,
and H series
Wt./C 128 lb


AN211



AN211HDG
AN211EG
AN211

Wt./C 181 lb


A212



Wt./C 113 lb

A212HDG
A212EG
A212
A212SS6


B210



B210HDG
B210EG
B210
B210SS6
Wt./C 65 lb

For attaching B and BR series.
Wt./C 65 lb


C210



C210HDG
C210EG
C210

For attaching C series channel.
Wt./C 77 lb


D210



For attaching D series channel.
Wt./C 71 lb

D210HDG
D210EG
D210
D210SS6


E210



E210HDGC
E210EG
E210
Wt./C 112 lb

For attaching E series channel.


AB245



AB245HDG
AB245EG
AB245

For attaching A and AR series double channel.
Wt./C 70 lb

AB288



*Finishes
HDG
GoldGalv®
EG

Cat. No.	Bolt Size	Wt./C lb
AB288-3/8*	3/8	37
AB288-1/2*	1/2	37
AB288-5/8*	5/8	37

Hole Spacing
Hole Spacing
Hole Size
Material
Material













13/16" From End
1-7/8" Centers
9/16" Diam.
1-5/8" Width
1/4" Thick

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)

Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

Fittings and Brackets**SECTION 3****Wing Fittings**

AW204  AW204HDG AW204EG AW204 Wt./C 76 lb	AW214  AW214HDG AW214EG AW214 Wt./C 115 lb	A217  A217H A217EG A217 Wt./C 155 lb
AW205L  AW205LHDG AW205LEG AW205L Wt./C 59 lb	AW205R  AW205RHDG AW205REG AW205R Wt./C 59 lb	AW215L  AW215LHDG AW215LEG AW215L Wt./C 98 lb
AW220  AW220HI AW220EG AW220 Wt./C 90 lb	AW224  AW224HDGC AW224EG AW224 Wt./C 147 lb	AW219  AW219HDGC AW219EG AW219 Wt./C 187 lb
AW226  AW226HDG AW226 Wt./C 113 lb	A218  A218HD A218EG A218 Wt./C 177 lb	AW228  AW2 AW2 AW228 Wt./C 230 lb

Standard Dimensions

Hole Spacing 13/16" From End
Hole Spacing 1-7/8" Centers
Hole Size 9/16" Diam.
Material 1-5/8" Width
Material 1/4" Thick

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)

Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

SECTION 3


Brackets

Fittings and Brackets

<p>S202</p> <p>*Finish HDG</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>B</th> <th>C</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S202-6*</td><td>6</td><td>5</td><td>—</td><td>75</td></tr> <tr><td>S202-9*</td><td>9</td><td>8</td><td>2</td><td>100</td></tr> <tr><td>S202-15*</td><td>15</td><td>14</td><td>18</td><td>175</td></tr> <tr><td>S202-21*</td><td>21</td><td>20</td><td>14</td><td>250</td></tr> <tr><td>S202-27*</td><td>27</td><td>26</td><td>20</td><td>325</td></tr> <tr><td>S202-33*</td><td>33</td><td>32</td><td>26</td><td>400</td></tr> </tbody> </table>	Cat. No.	A	B	C	Wt./C lb	S202-6*	6	5	—	75	S202-9*	9	8	2	100	S202-15*	15	14	18	175	S202-21*	21	20	14	250	S202-27*	27	26	20	325	S202-33*	33	32	26	400	<p>S203</p> <p>*Finishes HDG</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>B</th> <th>Design Load/lb</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S203-8*</td><td>8-1/2</td><td>4-1/16</td><td>1200</td><td>180</td></tr> <tr><td>S203-14*</td><td>14-1/2</td><td>5-3/8</td><td>1200</td><td>325</td></tr> <tr><td>S203-20*</td><td>20-1/2</td><td>6-11/16</td><td>1200</td><td>525</td></tr> <tr><td>S203-26*</td><td>26-1/2</td><td>8</td><td>1200</td><td>675</td></tr> <tr><td>S203-32*</td><td>32-1/2</td><td>8</td><td>1200</td><td>840</td></tr> <tr><td>S203-38*</td><td>38-1/2</td><td>8</td><td>1200</td><td>1050</td></tr> </tbody> </table>	Cat. No.	A	B	Design Load/lb	Wt./C lb	S203-8*	8-1/2	4-1/16	1200	180	S203-14*	14-1/2	5-3/8	1200	325	S203-20*	20-1/2	6-11/16	1200	525	S203-26*	26-1/2	8	1200	675	S203-32*	32-1/2	8	1200	840	S203-38*	38-1/2	8	1200	1050	<p>S249</p> <p>*Finishes HDG SS6C</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>B</th> <th>Design Load/lb</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S249-8*</td><td>8-1/2</td><td>8</td><td>1500</td><td>320</td></tr> <tr><td>S249-14*</td><td>14-1/2</td><td>9</td><td>1500</td><td>520</td></tr> <tr><td>S249-20*</td><td>20-1/2</td><td>9</td><td>1500</td><td>660</td></tr> <tr><td>S249-26*</td><td>26-1/2</td><td>11-1/2</td><td>1500</td><td>870</td></tr> <tr><td>S249-32*</td><td>32-1/2</td><td>11-1/2</td><td>1500</td><td>1030</td></tr> <tr><td>S249-38*</td><td>38-1/2</td><td>11-1/2</td><td>1500</td><td>1230</td></tr> </tbody> </table>	Cat. No.	A	B	Design Load/lb	Wt./C lb	S249-8*	8-1/2	8	1500	320	S249-14*	14-1/2	9	1500	520	S249-20*	20-1/2	9	1500	660	S249-26*	26-1/2	11-1/2	1500	870	S249-32*	32-1/2	11-1/2	1500	1030	S249-38*	38-1/2	11-1/2	1500	1230											
Cat. No.	A	B	C	Wt./C lb																																																																																																																		
S202-6*	6	5	—	75																																																																																																																		
S202-9*	9	8	2	100																																																																																																																		
S202-15*	15	14	18	175																																																																																																																		
S202-21*	21	20	14	250																																																																																																																		
S202-27*	27	26	20	325																																																																																																																		
S202-33*	33	32	26	400																																																																																																																		
Cat. No.	A	B	Design Load/lb	Wt./C lb																																																																																																																		
S203-8*	8-1/2	4-1/16	1200	180																																																																																																																		
S203-14*	14-1/2	5-3/8	1200	325																																																																																																																		
S203-20*	20-1/2	6-11/16	1200	525																																																																																																																		
S203-26*	26-1/2	8	1200	675																																																																																																																		
S203-32*	32-1/2	8	1200	840																																																																																																																		
S203-38*	38-1/2	8	1200	1050																																																																																																																		
Cat. No.	A	B	Design Load/lb	Wt./C lb																																																																																																																		
S249-8*	8-1/2	8	1500	320																																																																																																																		
S249-14*	14-1/2	9	1500	520																																																																																																																		
S249-20*	20-1/2	9	1500	660																																																																																																																		
S249-26*	26-1/2	11-1/2	1500	870																																																																																																																		
S249-32*	32-1/2	11-1/2	1500	1030																																																																																																																		
S249-38*	38-1/2	11-1/2	1500	1230																																																																																																																		
<p>S250</p> <p>*Finishes HDG SS6C</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>Design Load lb</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S250-6*</td><td>6</td><td>1500</td><td>150</td></tr> <tr><td>S250-8*</td><td>8-1/2</td><td>1500</td><td>150</td></tr> <tr><td>S250-12*</td><td>12</td><td>800</td><td>250</td></tr> <tr><td>S250-14*</td><td>14-1/2</td><td>800</td><td>250</td></tr> <tr><td>S250-18*</td><td>18</td><td>550</td><td>350</td></tr> <tr><td>S250-20*</td><td>20-1/2</td><td>550</td><td>350</td></tr> <tr><td>S250-24*</td><td>24</td><td>400</td><td>450</td></tr> <tr><td>S250-26*</td><td>26-1/2</td><td>400</td><td>450</td></tr> </tbody> </table> <p>May be installed inverted with no change in load ratings.</p>	Cat. No.	A	Design Load lb	Wt./C lb	S250-6*	6	1500	150	S250-8*	8-1/2	1500	150	S250-12*	12	800	250	S250-14*	14-1/2	800	250	S250-18*	18	550	350	S250-20*	20-1/2	550	350	S250-24*	24	400	450	S250-26*	26-1/2	400	450	<p>S251</p> <p>*Finishes HDGC SS6C</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>Design Load lb</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S251-12*</td><td>12</td><td>1650</td><td>514</td></tr> <tr><td>S251-14*</td><td>14-1/2</td><td>1650</td><td>514</td></tr> <tr><td>S251-18*</td><td>18</td><td>1050</td><td>714</td></tr> <tr><td>S251-20*</td><td>20-1/2</td><td>1050</td><td>714</td></tr> <tr><td>S251-24*</td><td>24</td><td>800</td><td>914</td></tr> <tr><td>S251-26*</td><td>26-1/2</td><td>800</td><td>914</td></tr> <tr><td>S251-30*</td><td>30</td><td>650</td><td>1114</td></tr> <tr><td>S251-32*</td><td>32-1/2</td><td>650</td><td>1114</td></tr> <tr><td>S251-36*</td><td>36</td><td>500</td><td>1314</td></tr> <tr><td>S251-38*</td><td>38-1/2</td><td>500</td><td>1314</td></tr> </tbody> </table>	Cat. No.	A	Design Load lb	Wt./C lb	S251-12*	12	1650	514	S251-14*	14-1/2	1650	514	S251-18*	18	1050	714	S251-20*	20-1/2	1050	714	S251-24*	24	800	914	S251-26*	26-1/2	800	914	S251-30*	30	650	1114	S251-32*	32-1/2	650	1114	S251-36*	36	500	1314	S251-38*	38-1/2	500	1314	<p>S256</p> <p>*Finishes HDGC SS6</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>A</th> <th>Design Load lb</th> <th>Wt./C lb</th> </tr> </thead> <tbody> <tr><td>S256-6*</td><td>6</td><td>1000</td><td>151</td></tr> <tr><td>S256-8*</td><td>8-1/2</td><td>1000</td><td>151</td></tr> <tr><td>S256-12*</td><td>12</td><td>500</td><td>251</td></tr> <tr><td>S256-14*</td><td>14-1/2</td><td>500</td><td>251</td></tr> <tr><td>S256-18*</td><td>18</td><td>300</td><td>351</td></tr> <tr><td>S256-20*</td><td>20-1/2</td><td>300</td><td>351</td></tr> <tr><td>S256-24*</td><td>24</td><td>250</td><td>451</td></tr> <tr><td>S256-26*</td><td>26-1/2</td><td>250</td><td>451</td></tr> </tbody> </table> <p>When installed in inverted position reduce load rating 40%.</p>	Cat. No.	A	Design Load lb	Wt./C lb	S256-6*	6	1000	151	S256-8*	8-1/2	1000	151	S256-12*	12	500	251	S256-14*	14-1/2	500	251	S256-18*	18	300	351	S256-20*	20-1/2	300	351	S256-24*	24	250	451	S256-26*	26-1/2	250	451
Cat. No.	A	Design Load lb	Wt./C lb																																																																																																																			
S250-6*	6	1500	150																																																																																																																			
S250-8*	8-1/2	1500	150																																																																																																																			
S250-12*	12	800	250																																																																																																																			
S250-14*	14-1/2	800	250																																																																																																																			
S250-18*	18	550	350																																																																																																																			
S250-20*	20-1/2	550	350																																																																																																																			
S250-24*	24	400	450																																																																																																																			
S250-26*	26-1/2	400	450																																																																																																																			
Cat. No.	A	Design Load lb	Wt./C lb																																																																																																																			
S251-12*	12	1650	514																																																																																																																			
S251-14*	14-1/2	1650	514																																																																																																																			
S251-18*	18	1050	714																																																																																																																			
S251-20*	20-1/2	1050	714																																																																																																																			
S251-24*	24	800	914																																																																																																																			
S251-26*	26-1/2	800	914																																																																																																																			
S251-30*	30	650	1114																																																																																																																			
S251-32*	32-1/2	650	1114																																																																																																																			
S251-36*	36	500	1314																																																																																																																			
S251-38*	38-1/2	500	1314																																																																																																																			
Cat. No.	A	Design Load lb	Wt./C lb																																																																																																																			
S256-6*	6	1000	151																																																																																																																			
S256-8*	8-1/2	1000	151																																																																																																																			
S256-12*	12	500	251																																																																																																																			
S256-14*	14-1/2	500	251																																																																																																																			
S256-18*	18	300	351																																																																																																																			
S256-20*	20-1/2	300	351																																																																																																																			
S256-24*	24	250	451																																																																																																																			
S256-26*	26-1/2	250	451																																																																																																																			
<p>S247</p> <p>Design Moment (channel upright as shown) When Supported By A-1200 5250 inch lb A-1400 3650 inch lb Applies to fitting only, not to the arm.</p> <p>S247HDG S247 S247SS6</p>	<p>S248</p> <p>Design Moment (channel upright as shown) When Supported By A-1202 10800 inch lb A-1402 7550 inch lb Applies to fitting only, not to the arm.</p> <p>S248HDGC S248</p>																																																																																																																					
<p>Standard Dimensions</p>	<p>Hole Spacing Hole Spacing Hole Size Material</p>	<p>13/16" From End 1-7/8" Centers 9/16" Diam. 1-5/8" Width</p>	<p>Materials</p>																																																																																																																			
<p>Thomas & Betts</p>	<p>HDG(C) EG(C) (No suffix) SS6(C)</p>	<p>Hot-Dipped Galvanized Electrogalvanized GoldGalv® Stainless Steel 316</p>	<p>Wt./C 229 lb</p>																																																																																																																			
<p>26</p>			<p>Wt./C 272 lb</p>																																																																																																																			


Fittings and Brackets**Brackets**

S204 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>750</td></tr> <tr><td>A-1400</td><td>500</td></tr> </table> <p>S204HDGC S204 Wt./C 174 lb</p>	A-1200	750	A-1400	500	S205 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>750</td></tr> <tr><td>A-1400</td><td>500</td></tr> </table> <p>S205HDGC S205 Wt./C 264 lb</p>	A-1200	750	A-1400	500	S217 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>750</td></tr> <tr><td>A-1400</td><td>650</td></tr> </table> <p>S217HDG S217 S217SS6 Wt./C 264 lb</p>	A-1200	750	A-1400	650
A-1200	750													
A-1400	500													
A-1200	750													
A-1400	500													
A-1200	750													
A-1400	650													
S218 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>750</td></tr> <tr><td>A-1400</td><td>650</td></tr> </table> <p>S218HDG S218 Wt./C 295 lb</p>	A-1200	750	A-1400	650	S222 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>1000</td></tr> <tr><td>A-1400</td><td>750</td></tr> </table> <p>S222HDG S222 Wt./C 385 lb</p>	A-1200	1000	A-1400	750	S226 <p>Design Uniform Load/lb</p> <table border="1"> <tr><td>A-1200</td><td>1000</td></tr> <tr><td>A-1400</td><td>750</td></tr> </table> <p>S226HDG S226 Wt./C 421 lb</p>	A-1200	1000	A-1400	750
A-1200	750													
A-1400	650													
A-1200	1000													
A-1400	750													
A-1200	1000													
A-1400	750													

SECTION 3**Fittings and Brackets****Post Bases****AP232**


AP232HDGC
AP232EG
AP232

Wt./C 384 lb

AP235


AP235HDGC
AP235EG
AP235

Wt./C 400 lb

AP232SQ


AP232SQHDG
AP232SQEG
AP232SQSS6

Wt./C 384 lb


AP235SQ

AP235SQHDG
AP235SQEG
AP235SQ
AP235SQSS6

Wt./C 400 lb


SECTION 3**Fittings and Brackets****Special Application Fittings and Brackets****AN270***Finishes
HDG
EG

Cat. No.	A	B	Wt./C lb
AN270-1*	2-3/8	6	113
AN270-2*	4-3/8	8	151
AN270-3*	6-3/8	10	199
AN270-4*	8-3/8	12	246
AN270-*	10-3/8	14	293

TS272**Track Support**


Requires 3/8" x 2-1/2" bolt and nut (not included). Design load: 1000 lb Wt./C 104 lb

TS272HDG


TS273**Track Support**

For use over channel splice. Requires 3/8" x 2-1/2" bolt and nut (not included). Design load: 2000 lb Wt./C 228 lb

TS273HDG

TR292**Can be used for series A, E and H channels only.**


Standard finish is Electrogalvanized Frictionless needle bearings. Design load: 500 lb Safety factor of 5. Wt./C 59 lb

TR294

* Do not use with back to back Strut

Can be used for series A, E and H channels only.

Standard finish is Electrogalvanized Frictionless needle bearings. Design load: 1000 lb Safety factor of 5. Wt./C 106 lb

C728**Pipe Roller (Pair)**

Cast aluminum rollers, steel brackets. Designed for standard saddles. Order separately for each pair of rollers: - Two 1/2" x 5/16" hex head cap screws and two 1/2" channel nuts. Space to suit O.D. of pipe and wrapping. Wt./C : 300 lb Design Load: 2350 lb

Standard Dimensions

Hole Spacing
Hole Spacing
Hole Size
Material

13/16" From End
1-7/8" Centers
9/16" Diam.
1/4" Thick

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)


Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

Thomas & Betts



SECTION 4 **BEAM CLAMPS**

Thomas & Betts



Material

Most products are manufactured from hot rolled carbon steel bars or hot rolled strip steel. Pipe rollers are cast iron.

Design Loads

Where design loads are indicated, they provide for a safety factor of 3 in conformance with the American Standard Code for Pressure Piping. For more information, see section 8 Engineering Data and Specifications.

Finishes and Special Materials

Hot-Dipped Galvanized (HDGC) is standard for all Superstrut® beam clamps. The material is zinc coated after fabrication providing total product protection on all surfaces. The fabricated beam clamps are suspended and then dipped into tanks of hot zinc for a prolonged period, creating a coherent bond.


Selected beam clamps can also be available in GoldGalv® (no suffix) or Stainless Steel Type 316 (SS6C). Contact your Regional Sales Office for availability and minimum quantities.

SECTION 4

Beam Clamps

Beam Clamps for Mounting Channel

<p>U501, U502</p> <p>*Finishes HDG EG GoldGalv® SS6C</p> <p>furnished complete Design Load U501 : 2150 lb U502 : 3000 lb</p> <table border="1"> <thead> <tr> <th>Cat. No.</th> <th>For Channel</th> <th>A</th> <th>Wt./C</th> </tr> </thead> <tbody> <tr> <td>U501*</td> <td>A1200 A1400 B1200 B1400 C1200 B1402</td> <td>3-3/16</td> <td>90</td> </tr> <tr> <td>U502*</td> <td>A1202 A1402 C1202 H1200</td> <td>4-13/16</td> <td>100</td> </tr> </tbody> </table>	Cat. No.	For Channel	A	Wt./C	U501*	A1200 A1400 B1200 B1400 C1200 B1402	3-3/16	90	U502*	A1202 A1402 C1202 H1200	4-13/16	100	<p>U504</p> <p>U504</p> <p>Can be used with all channels.</p> <p>U504HDG U504EG U504 U504SS6</p> <p>Wt./C 140 lb</p>	<p>U505</p> <p>U505</p> <p>Can be used with all channels.</p> <p>U505HDG U505EG U505</p> <p>Wt./C 270 lb</p>
Cat. No.	For Channel	A	Wt./C											
U501*	A1200 A1400 B1200 B1400 C1200 B1402	3-3/16	90											
U502*	A1202 A1402 C1202 H1200	4-13/16	100											
<p>U510</p> <p>1/2" x 1-1/2" set screw included. Order separately one 1/2" x 1-1/2" hex head cap screw and 1/2" channel nut.</p> <table border="1"> <thead> <tr> <th>Design Load lb</th> <th>Channel</th> </tr> </thead> <tbody> <tr> <td>1000</td> <td>A1200</td> </tr> <tr> <td>800</td> <td>A1400</td> </tr> </tbody> </table> <p>U510HDGC U510EG U510 U510SS6</p> <p>Wt./C 75 lb</p>	Design Load lb	Channel	1000	A1200	800	A1400	<p>512U</p> <p>Order separately one 1/2" x 1-1/2" hex head cap screw and 1/2" channel nut.</p> <table border="1"> <thead> <tr> <th>Design Load lb</th> <th>Channel</th> </tr> </thead> <tbody> <tr> <td>1000</td> <td>A1200</td> </tr> <tr> <td>800</td> <td>A1400</td> </tr> </tbody> </table> <p>512UHDG 512UEG 512U</p> <p>Wt./C 26 lb</p>	Design Load lb	Channel	1000	A1200	800	A1400	<p>U514</p> <p>3/8" x 1-1/2" set screw included. Design Load 750 lb/pair</p> <p>U514HDGC U514EG U514 U514SS6</p> <p>Wt./C 40 lb</p>
Design Load lb	Channel													
1000	A1200													
800	A1400													
Design Load lb	Channel													
1000	A1200													
800	A1400													
<p>U514-A</p> <p>1/2" x 1-1/2" set screw included. Design Load 1650 lb/pair</p> <p>U514-AHDGC U514-AEG U514-A U514-ASS6</p> <p>Wt./C 59 lb</p>	<p>U515</p> <p>For all A series channel. 1/2" x 1-1/2" set screw included. Design Load 800 lb</p> <p>U515HDGC U515EG U515 U515SS6</p> <p>Wt./C 95 lb</p>	<p>U515-B</p> <p>For all B series channel. 1/2" x 1-1/2" set screw included. Design Load 800 lb</p> <p>U515BHDG U515BEG U515B U515BSS6</p> <p>Wt./C 91 lb</p>												

Beam Clamps**Beam Clamps for Mounting Channel****U520****U521****U522**


*Finishes
GoldGalv®
EG

Nuts, cap screws and
set screws included.

Cat. No.	Flange Width	Design		
		A	Wt./C lb	Load lb
U520*	2-3/8 - 4-1/2	8-3/4	328	2000
U521*	3-3/4 - 5-3/4	10	343	1300
U522*	5-5/8 - 7-5/8	11-7/8	353	900

U544


Single Adjusting Screw
End Cap Set



Should be ordered
as one set.

U544EG**U543**

Adjusting Screw End Caps




U543HDG
U543EG
U543

Should be ordered
in multiples of two (2).

Wt./C 44 lb

A597


*Finishes
HDGC
SS6



Cat. No.	Channel Series	Design	
		A	F
A597*	A	108	800

U570-1
U570-2

*Finish
HDGC



Cat. no.	Design			
	A in.	F in.	Wt./C lbs	Load lbs
U570-1*	1-1/2	4 to 9	240	800
U570-2*	1-1/2	7 to 17	300	800

Materials
HDG(C)
EG(C)
(No suffix)
SS6(C)

Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316

Thomas & Betts

SECTION 4


Beam Clamps

Beam Clamps for Hanging Rod

U562

Beam Clamp


Optional Use of U562HDG Beam Clamp



E146 square nut order separately.
1/2" set screw included.

Rod Size	Wt./C lb	Design Load lb
1/2	80	800

U562HDG
U562EG
U562
U562SS6




1/2" set screw included.

For 20° swivel application use ES-145-1/2 nut.

UM562

Beam Clamp

UM562HDGC
UM562EG
UM562
UM562SS6



E146 square nut order separately.
1/2" set screw included.


Rod Size	Wt./C lb	Design Load lb
1/2	100	1200

For 20° swivel application use
ES-145-1/2 nut.

US562

Beam Clamp with Swing Hanger

US562HDG
US562EG
US562




1/2" set screw included.

U563

Beam Clamp


Optional Use of U563HDG Beam Clamp



Square nut order separately.
3/8" set screw included.

Rod Size	Wt./C lb	Design Load lb
3/8	33	400

U563HDG
U563EG
U563




3/8" set screw included.

US563

Beam Clamp with Swing Hanger

US563HDG
US563




3/8" set screw included.

Cat. No.	A Size	Wt./C lb	Design Load lb
U569	3/8	150	400

U569HDG
U569


Beam Clamp



Maximum flange width 5".

A570

Beam Clamp with Safety Rod




Flange width 4" min. - 8" max.
For use with 3/8" rod see U-569.

Cat. No.	A Size	Wt./C lb	Design Load lb
A570HDG	1/2	220	500

Beam Clamps**Beam Clamps for Hanging Rod****U560**

Heavy Duty Beam Clamp




*Finishes
GoldGalv®
EG

Cat. No.	A	B	C	Wt./C lb	Design Load lb
U560-1/4*	1/4	1/8	3/8 x 1-1/2	67	1050
U560-3/8*	3/8	1/8	3/8 x 1-1/2	67	1050
U560-1/2*	1/2	1/4	1/2 x 1-1/2	130	2650
U560-5/8*	5/8	1/4	1/2 x 1-1/2	130	2650

U564

Heavy Duty Beam Clamp




*Finishes
GoldGalv®
EG

Cat. No.	A	B	C	Wt./C lb	Design Load lb
U564-3/8*	3/8	1/8	3/8 x 2-3/4	109	1300
U564-1/2*	1/2	1/4	1/2 x 2-3/4	201	3150
U564-5/8*	5/8	1/4	1/2 x 2-3/4	201	3150

U568

Beam Clamp Safety Strap




For U563 beam clamp.

Cat. No.	Beam Flange Width	A	Wt./C lb
U568-1EG	6	8	18
U568-2EG	9	11	28

16 gauge material

U568

Beam Clamp Safety Strap




For U562 and UM562 beam clamp.

Cat. No.	Beam Flange Width	A	Wt./C lb
U568-3EG	6	9	25
U568-4EG	9	12	33
U568-5EG	12	15	42

16 gauge material

U568

Beam Clamp Safety Strap




For U560 and U564 beam clamp.

Cat. No.	Beam Flange Width	A	Wt./C lb
U568-6EG	6	9	24
U568-7EG	9	12	31
U568-8EG	12	15	44


16 gauge material

C775L / M775L

Clamp with Lock Nut



C775L



M775L

Standard Finish - Electrogalvanized (EG)

Malleable Iron (M775L)
Carbon Steel (C775L)

Cat. No.	Rod Size	Dimensions in.			Wt./C lb	Design Load lb
		A	B	C		
C775L-3/8EG	3/8	3/8	3/8	3/4	38	400
C775L-1/2EG	1/2	3/8	3/8	3/4	39	500
C775L-5/8EG	5/8	1/2	1/2	3/4	60	550
C775L-3/4EG	3/4	5/8	5/8	3/4	69	600
C775L-7/8EG	7/8	3/4	3/4	1	184	900
M775L-3/8EG	3/8	3/8	3/4	1-3/4	27	400
M775L-1/2EG	1/2	1/2	3/4	1-3/4	35	400
M775L-5/8EG	5/8	5/8	3/4	2	52	440
M775L-3/4EG	3/4	3/4	3/4	2	63	500

Complies to Specification MSS SP69, Type 23.

Materials

HDG(C)
EG(C)
(No suffix)
SS6(C)Hot-Dipped Galvanized
Electrogalvanized
GoldGalv®
Stainless Steel 316**Thomas & Betts**

SECTION 4

Beam Clamps

Beam Clamps for Hanging Rod

500SC, 502, 503SC, 507,

508, 509, 510, 511

Beam Clamp




*Standard Finish -
Electrogalvanized (no suffix)*

Cat. No.	Tapped Holes	Base Dim. in.		Jaw Opening	Wt./C lb	Design Load lb
		A	B			
500SC	1/4 - 20	1	1-1/4	15/16	18	450
502	3/8 - 16	2	2	1	92	1300
503SC	1/2 - 13	2-5/8	2-1/2	1	164	1300
507	1/2 - 13	2-1/2	2-3/8	1-3/8	165	1700
508	1/2 - 13	2-1/2	2-3/8	2-1/8	184	1700
509	10 - 24	1	1-1/4	15/16	22	375
510	1/4 - 20	27/32	1-1/8	5/8	15	400
511	10 - 24	27/32	1-1/8	5/8	15	400


6H Series in combination with 500 series Beam Clamp

Conduit and Pipe Hanger



Features


- Accommodates 1/2" through 4" EMT or rigid conduit
- Can be used for either vertical or horizontal installation
- 6H-TB Series is threaded so there are less parts to handle or drop
- Installs easily with a screwdriver




6H Series
without bolt
Fig. 1



6H--B Series
with bolt and hex nut
Fig. 2



6H-T Threaded Series
threaded without bolt
Fig. 3




6H-TB Threaded Series
threaded with bolt
Fig. 4

Without Bolt		With Bolt		EMT	Rigid Conduit or Pipe	Qty. per Box
Cat. No.	Fig. No.	Cat. No.	Fig. No.			
6H0	1	6H0-B	2	1/2"	3/8"-1/2"	100
6H0-T	3	6H0-TB	4	1/2"	3/8"-1/2"	100
6H1	1	6H1-B	2	3/4"	3/4"	100
6H1-T	3	6H1-TB	4	3/4"	3/4"	100
6H2	1	6H2-B	2	1"	1"	100
		6H2-TB	4	1"	1"	100
6H2 1/2	1	6H2 1/2B	2	1-1/4"	-	100
		6H2 1/2-TB	4	1-1/4"	-	100
6H3-SC	1	6H3-B	2	1-1/2"	1-1/4"	100
		6H3-TB	4	1-1/2"	1-1/4"	100
6H4	1	6H4-B	2	-	1-1/2"	100
		6H4-TB	4	-	1-1/2"	100
6H5	1	6H5-B	2	2"	2"	100
		6H5-TB	4	2"	2"	100
6H6	1	6H6-B	2	2-1/2"	2-1/2"	100
6H7	1	6H7-B	2	3"	3"	100
6H8	1	6H8-B	2	3-1/2"	3-1/2"	100
6H9	1	6H9-B	2	4"	4"	100

Standard Finish - Electrogalvanized (no suffix). Use SS suffix for Stainless Steel.

Load rating: 500 lb with a safety factor of 3. (For weight per 100 see page 46)

Beam Clamps**Beam Clamps for Mounting Pipe and Conduit****U571****U572****Conduit Clamp**


For attaching 1/2" thru 1-1/2" conduit to beam, channel, angle or column. Secures conduit to the support parallel or at right angles to it.

5/16" set screw
12 gauge material

Standard Finish - GoldGalv®


Wt./C 38 lb

Cat. No.	Conduit Size	Max. Flange Thickness	Dim. A	Wt./C lb
U571	1/2	1	1-3/4	36
	3/4	3/4	1-3/4	36
	1	1/2	1-3/4	36
U572	3/4	1-1/2	2-1/2	59
	1	1-1/4	2-1/2	59
	1-1/4	1	2-1/2	59
	1-1/2	5/8	2-1/2	59

Pipe Supports


Type RC and RCS

- Malleable Iron
- For mounting pipe or conduit at right angles to the beam
- Use SS316 suffix for 316 Stainless Steel
- Use HDG suffix for Hot-Dipped Galvanized



Type EC

- Malleable Iron
- For mounting pipe or conduit vertically across the beam
- Use HDG suffix for Hot-Dipped Galvanized
- CSA Certified



Type PC

- Malleable Iron
- For mounting pipe or conduit parallel to the beam
- Use SS316 suffix for 316 Stainless Steel
- Use HDG suffix for Hot-Dipped Galvanized

Pipe Supports

Three types of pipe clamps are available to provide right angle, vertical and parallel attachment to a beam. Types RC, EC and PC are malleable iron clamps with an edge that grips the structural member for maximum holding power when tightened.

Type RCS clamps are all steel, providing two bearing surfaces for strong attachment for mounting pipe or conduit at right angles to the beam.

All parts are electrogalvanized (no suffix) including the threads. The clamps are designed for clamping to a wide variety of beam thicknesses and tapers. Can be installed using only a wrench.

Dimensions in inches				
Cat No. & Size	O.D. of Conduit or Pipe	Nom. Conduit or Pipe Size	Std. Ctn.	Wt./C lb
RCS-3/8	.675	3/8	50	31
RCS-1/2	.840	1/2	50	34
RCS-3/4	1.050	3/4	50	39
RCS-1	1.315	1	50	42
RCS-1-1/4	1.660	1-1/4	50	43
RCS-1-1/2	1.900	1-1/2	50	60
RCS-2	2.375	2	50	72
RC-1/2	.840	1/2	50	36
RC-3/4	1.050	3/4	50	43
RC-1	1.315	1	50	49
RC-1-1/4	1.660	1-1/4	50	51
RC-1-1/2	1.900	1-1/2	50	54
RC-2-SC	2.375	2	50	76
RC-2-1/2	2.875	2-1/2	25	107
RC-3	3.500	3	25	116
RC-3-1/2	4.000	3-1/2	25	134
RC-4-SC	4.500	4	20	158
EC-1/2	.840	1/2	50	69
EC-3/4	1.050	3/4	50	78
EC-1	1.315	1	25	83
EC-1-1/4	1.660	1-1/4	25	108
EC-1-1/2	1.900	1-1/2	25	112
EC-2	2.375	2	25	140
EC-2-1/2	2.875	2-1/2	10	183
EC-3	3.500	3	10	203
PC-3/8	.675	3/8	50	32
PC-1/2	.840	1/2	50	53
PC-3/4	1.050	3/4	50	53
PC-1	1.315	1	50	61
PC-1-1/4	1.660	1-1/4	25	79
PC-1-1/2	1.900	1-1/2	25	56
PC-2	2.375	2	25	116
PC-2-1/2	2.875	2-1/2	25	148
PC-3	3.500	3	10	175
PC-3-1/2	4.00	3-1/2	10	199
PC-4	4.500	4	10	224


SECTION 4

Beam Clamps

Beam Fittings

C781

Square Washer



*Finishes
B
HDG
EG
SS6


STD
PACK:
50

Used for beam applications.
For channel applications use AB241.

Cat. No.	Rod Size	Hole Size	Overall Dimensions	Wt./C lb
C781-3/8*	3/8	7/16	3 x 3 x 3/16	27
C781-1/2*	1/2	9/16	3 x 3 x 3/16	27
C781-5/8*	5/8	11/16	3 x 3 x 1/4	47
C781-3/4*	3/4	13/16	3 x 3 x 1/4	42
C781-7/8*	7/8	15/16	4 x 4 x 3/8	85
C781-1*	1	1-1/8	4 x 4 x 3/8	160

M742R

Ceiling Flange




*Finishes
B
EG

Cat. No.	Rod Size	Wt./C lb
M742R-3/8*	3/8	16
M742R-1/2*	1/2	16

540


Side Beam Hanger Clip



*Finishes
B
EG
GoldGalv®

542

Side Beam Hanger Clip




Standard Finish - GoldGalv®
For 3/8" and 1/2" rods.

Cat. No.	A	B	C	D	Wt./C lb
540-3/8*	7/16	1-7/8	1/4	7/8	38
540-1/2*	9/16	1-7/8	1/4	1-5/8	36
540-5/8*	11/16	2-1/2	3/8	2	84
540-3/4*	13/16	2-1/2	3/8	2	113

Cat. No.	Rod Size	Design Load		Wt./C lb
		lb	lb	
542-3/8	3/8	610	35	
542-1/2	1/2	1000	38	

S541

Swing Connector




3/8" x 1-3/4" bolt,
nut and clevis
included.

Standard Finish - GoldGalv®
For use with wood beam.

Cat. No.	Rod Size	Wt./C lb
S541-3/8	3/8	31

Beam Clamps**Beam Fittings****U577**

Clevis and Swing Connector


**Standard Finish - GoldGalv®**

For use with wood beam.

Cat. No.	Rod Size	Wt./C lb
U577-1/2	1/2	69

U576

Hanger Clevis


**Standard Finish - GoldGalv®**

For rods up to 1/2"
Mounting holes 7/16" diameter.
For use with wood beam.

Cat. No.	Material		
	Hole A	B	Thickness Wt./C lb
U576-3/8	7/16	3/16	27
U576-1/2	9/16	3/16	27

U579

Ceiling Flange

**Standard Finish - GoldGalv®**


Malleable Iron
Nuts and wood screws not included.
Mounting holes 13/32"

Cat. No.	Wt./C	
	A	lb
U579-3/8	3-1/2	30
U579-1/2	4-1/4	50



SECTION 5
**PIPE STRAPS, PIPE CLAMPS
AND HANGERS**

Thomas & Betts

Pipe Straps, Pipe Clamps and Hangers**Material**

Most products are manufactured from hot rolled carbon steel bars or hot rolled strip steel. Pipe rollers are cast iron.

Design Loads

Where design loads are indicated, they provide for a safety factor of 3 in conformance with the American Standard Code for Pressure Piping.

Hanger Design


Pipe hangers are of advanced design to be user friendly.

Finishes and Special Materials

The standard finish is Electrogalvanized (EGC) or GoldGalv®. Some products are offered in Aluminum and Stainless Steel where noted.

SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Conduit and Cable Clamps****701****O.D. Pipe and Conduit Clamp**

Machine screw and nut included.



Cat. No.	O.D. of pipe		Rigid	EMT	Wt./C.	Std
	in.	mm	Cond.	Cond.	lb	Pack
701-045PG	.36-.45	9-11.5	—	—	9	10
701-055PG	.46-.55	11.5-14	—	—	10	10
701-065PG	.56-.65	14-17	—	—	11	10
701-075PG	.66-.75	17-19.5	—	1/2	13	10
701-088PG	.76-.88	19.5-22.5	1/2	—	15	10
701-100PG	.89-1.00	22.5-25.4	—	3/4	16	10
701-113PG	1.01-1.13	25.5-29	3/4	—	17	10
701-126PG	1.14-1.26	29-32	—	1	18	10
701-140PG	1.27-1.40	32-36	1	—	18	10
701-153PG	1.41-1.53	36-39	—	1-1/4	19	10
701-167PG	1.54-1.67	39-42.5	1-1/4	—	20	10
701-180PG	1.68-1.80	42.5-46	—	1-1/2	23	10
701-193PG	1.81-1.93	46-49	1-1/2	—	26	10
701-204PG	1.93-2.04	49-52	—	—	30	10
701-225PG	2.10-2.25	53-57.5	—	2	32	10
701-237PG	2.26-2.37	57.5-60	2	—	34	10
701-245PG	2.33-2.45	59.95-62.5	—	—	36	10
701-257PG	2.46-2.57	62.5-65.5	—	—	38	10
701-287PG	2.75-2.87	70-73	2-1/2	2-1/2	40	10
701-294PG	2.88-2.94	73-75	—	—	42	10
701-306PG	2.95-3.06	75-78	—	—	42.5	10
701-319PG	3.07-3.19	78-81	—	—	43	10
701-350PG	3.36-3.50	85.5-89	3	3	45	10
701-356PG	3.51-3.56	89-90	—	—	46	10
701-379PG	3.70-3.79	94-96.5	—	—	48	10
701-400PG	3.80-4.00	96.5-101.5	3-1/2	3-1/2	49	10
701-450PG	4.25-4.50	108-114	4	4	70	10
701-556PG	5.25-5.56	121-141	5	5	75	5
701-665PG	6.25-6.65	146-170	6	6	80	5
701-876PG	8.50-8.75	197-222	8	8	85	5


Standard Finishes and Materials

PG = Pregalvanized (i.e. 701-045PG)

AL = Aluminum (i.e. 701-045AL)
with zinc plated hardware

SS6 = Stainless Steel Type 316 (i.e. 701-045SS6)

FG = Fiberglass (in conduit sizes 1/2 to 4")

703**Universal Clamp**

Cat. No.	EMT/ Rigid	Conduit O.D.	Material Thickness	WT./C. lb	Std. Ctn.
703-1/2EG	1/2	.706 - .840	16 ga.	400	100
703-3/4EG	3/4	.932 - 1.050	14 ga.	550	100
703-1EG	1	1.163 - 1.315	14 ga.	550	100
703-1-1/4EG	1-1/4	1.508 - 1.660	14 ga.	800	50
703-1-1/2EG	1-1/2	1.738 - 1.900	14 ga.	800	50
703-2EG	2	2.195 - 2.375	14 ga.	800	50

Standard Finishes -


GoldGalv® (i.e.) 703-1/2

Electrogalvanized (EG suffix) (i.e.) 703-1-1/2EG


One size fits both Rigid and Electric Metal Tubing (EMT). Individually assembled with screw and nut.

Pipe Straps, Pipe Clamps and Hangers**Conduit and Cable Clamps****Quick Clamp II**

Design Load 1 has a safety factor of 4. Design Loads 2 and 3 have a safety factor of 1.

Ordering information


Cat. No.	Dimension A EMT in. (mm)	Dimension A Rigid Conduit in. (mm)	Quantity per Box	Wt./C lb	Design Load 1 Static Load Limit lb (kg)	Design Load 2 lb (kg)	Design Load 3 lb (kg)
TBQC050	1-5/16 (33.5)	1-1/4 (31.5)	100	10	200 (90)	50 (23)	50 (23)
TBQC075	1-3/4 (44.5)	1-11/16 (43)	100	12	200 (90)	50 (23)	50 (23)
TBQC100	1-13/16 (46)	1-3/4 (44.5)	100	13	200 (90)	50 (23)	50 (23)
TBQC125	2-1/8 (54)	2 (51)	50	15	200 (90)	50 (23)	50 (23)
TBQC150	2-3/8 (60.5)	2-3/16 (55.5)	50	16	200 (90)	50 (23)	50 (23)
TBQC200	2-5/8 (66.5)	2-1/2 (63.5)	50	19	200 (90)	50 (23)	50 (23)
TBQC250	3-1/16 (78)	3-1/16 (78)	25	29	350 (158)	50 (23)	50 (23)
TBQC300	3-11/16 (93.5)	3-11/16 (93.5)	25	34	350 (158)	50 (23)	50 (23)
TBQC350	4-3/16 (106.5)	4-3/16 (106.5)	25	38	350 (158)	50 (23)	50 (23)
TBQC400	4-11/16 (119)	4-11/16 (119)	25	42	350 (158)	50 (23)	50 (23)

Loading Data**Cobra**


Standard material is commercial-grade, bright electrogalvanized steel. Stainless steel 316L is also available; add the suffix "SS6" to catalogue no. (i.e.: CPC050SS6). Stainless steel bolt head is hexagonal and slotted only. Not available in aluminum.

Ordering information


Cat. N°	EMT Trade Size	Rigid Con. Trade Size	Cable O.D. Range (in.)	Limit (lb) Safety Factor = 4	Qty per Box	Wt./C lb
CPC050	1/2	1/2	0.650 - 0.890	200	100	10
CPC075	3/4	3/4	0.860 - 1.110	200	100	12
CPC100	1	1	1.100 - 1.400	200	100	14
CPC125	1 1/4	1 1/4	1.400 - 1.725	200	50	16
CPC150	1 1/2	1 1/2	1.690 - 1.980	200	50	18
CPC200	2	2	1.980 - 2.576	200	50	24
CPC250	2 1/2	2 1/2	2.576 - 3.060	350	25	36
CPC300	3	3	3.060 - 3.626	350	25	42
CPC350	3 1/2	3 1/2	3.626 - 4.126	350	25	46
CPC400	4	4	4.126 - 4.626	350	25	50

King Cobra**Ordering information**

Cat. N°	EMT Trade Size	Rigid Con. Trade Size	Cable O.D. Range (in.)	Qty per Box	Wt./C lb
LKCPC050	1/2	1/2	0.650 - 0.890	100	15
LKCPC075	3/4	3/4	0.860 - 1.110	100	16
LKCPC100	1	1	1.100 - 1.400	50	19
LKCPC125	1 1/4	1 1/4	1.400 - 1.725	50	23
LKCPC150	1 1/2	1 1/2	1.690 - 1.980	50	27
LKCPC200	2	2	1.980 - 2.576	50	38
LKCPC250	2 1/2	2 1/2	2.576 - 3.060	25	44
LKCPC300	3	3	3.060 - 3.626	25	53
LKCPC350	3 1/2	3 1/2	3.626 - 4.126	25	58
LKCPC400	4	4	4.126 - 4.626	25	66

Loading Data

Design Load 1 Static Load Limit lb (kg)	Design Load 2 lb (kg)	Design Load 3 lb (kg)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
350 (159)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)
450 (204)	50 (23)	50 (23)

SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Conduit and Cable Clamps****CH118****Heavy Duty Cable Clamp**

Cat. No.	O.D. of cable or pipe in.	O.D. mm	Rigid Cond.	EMT Cond.	Wt./C. lb
CH118-047EG	0.27-0.47	7.5-12	—	—	7
CH118-055EG	0.40-0.55	10-14	—	—	8
CH118-081EG	0.50-0.81	13-21	1/2	1/2	9
CH118-110EG	0.70-1.10	18-28	3/4	3/4	17
CH118-125EG	0.85-1.25	22-27	3/4	1	18
CH118-135EG	1.00-1.35	26-36	1	1	19
CH118-175EG	1.33-1.75	34-44	1-1/4	1-1/2	21
CH118-205EG	1.65-2.05	42-52	1-1/2	—	24
CH118-250EG	2.12-2.50	54-64	2	—	48
CH118-300EG	2.60-3.00	66-76	2-1/2	—	54
CH118-325EG	2.75-3.25	70-82	—	—	65
CH118-375EG	3.25-3.75	82-94	3	—	105
CH118-425EG	3.75-4.25	94-110	3-1/2	—	113
CH118-475EG	4.25-4.75	110-120	4	—	124

Standard Finishes:

Electrogalvanized (EG)

Aluminum (AL) comes complete with Stainless Steel


Type 304 saddle and hardware

Stainless Steel Type 316 clamp comes with Type 304 stainless steel hardware.

Available in double or triple configurations.

Example: Double - CH128-047EG

Triple - CH138-047EG


CB118 Counterbed**EB118 Extended Bed****DB118 Double Bed**

Cat. No.	Wt./C. lb
Counterbed	
CB118-047PG	1
CB118-055PG	1
CB118-070PG	1-1/2
CB118-090PG	2
CB118-110PG	3-1/2
CB118-140PG	4
CB118-175PG	4-1/2
CB118-200PG	5
CB118-250PG	11
CB118-300PG	13
Extended Bed	
EB118-047PG	4
EB118-055PG	4-1/2
EB118-070PG	5-1/2
EB118-090PG	6
EB118-110PG	13-1/2
EB118-140PG	16
EB118-175PG	17
EB118-200PG	20
EB118-250PG	30
EB118-300PG	38
Double Bed	
DB118-047PG	2
DB118-055PG	2
DB118-070PG	3
DB118-090PG	3

Standard Finishes -
Pregalvanized (PG)

Pipe Straps, Pipe Clamps and Hangers

Conduit and Cable Clamps

A716 Snap•Guard® Cushioned Clamp Tube Series**P716** Snap•Guard® Cushioned Clamp Pipe Series*Standard Finishes GoldGalv®**Available in Stainless Steel - use SS suffix.**(i.e) A716-1SS**Electrogalvanized (Silver) - use EG suffix.**(i.e) A716-1EG*


A716 / P716

- Assembly consisting of GoldGalv® finish steel clamp with bolt/locknut and cushion.
- Secure pipes, tubes and hoses for fluid conductors.
- Installation is easy and requires no more time than a simple pipe clamp installation.
- Cushion absorbs the shocks and associated vibrations from fluid surges in tubes, pipes and hoses.
- It can handle temperatures from 149°C to -40°C (300°F to -40°F).
- Cushioned Clamp assemblies are available individually bagged.

Assembly Cat. No.	Tubing			Standard Pipe		
	Tube O.D.	Wt./C lb	Assembly Cat. No.	Nominal Pipe Size	Std. Ctn.	Wt./C lb
A716-1/4	1/4	10	P716-1/4	1/4	25	10
A716-3/8	3/8	14	P716-3/8	3/8	25	14
A716-1/2	1/2	16	P716-1/2	1/2	25	16
A716-5/8	5/8	16	P716-3/4	3/4	25	18
A716-3/4	3/4	18	P716-1	1	25	22
A716-7/8	7/8	18	P716-1-1/4	1-1/4	25	27
A716-1	1	22	P716-1-1/2	1-1/2	10	36
A716-1-1/8	1-1/8	24	P716-2	2	10	43
A716-1-1/4	1-1/4	27	P716-2-1/2	2-1/2	10	49
A716-1-3/8	1-3/8	27	P716-3	3	10	60
A716-1-1/2	1-1/2	36	P716-3-1/2	3-1/2	10	62
A716-1-5/8	1-5/8	37	P716-4	4	10	94
A716-1-3/4	1-3/4	37	-	-	10	
A716-1-7/8	1-7/8	43	-	-	10	
A716-2	2	43	-	-	10	
A716-2-1/8	2-1/8	44	-	-	10	
A716-2-3/8	2-3/8	49	-	-	10	
A716-2-5/8	2-5/8	53	-	-	10	
A716-3-1/8	3-1/8	62	-	-	10	
A716-4-1/8	4-1/8	94	-	-	10	

U716, U717

Two Hole Cushioned Clamp



U716 / U717


- Guides, protects, and uniformly spaces line runs. Low cost, time saving method of attaching tubing and hose to equipment.
- Cushion is built to withstand the effects of most oils, chemical and industrial cleaning compounds, in temperatures from -45°C to 121°C (-50°F to 275°F). Interlock edge insures cushion remains in place.
- Attached with two standard fasteners to any flat surface, this clamp eliminates the use of special channels, providing a savings in both space requirements and cost.
- Cushioned clamps reduce vibration, shock, and noise in fluid systems and eliminates electrolysis.

Assembly Cat. No.	Copper and Steel Tubing O.D.	Copper Water Pipe (nom.)	Nominal Pipe Size	Std. Ctn.	Wt./C lb
U716-1/4	1/4	-	-	25	3
U716-3/8	3/8	1/4	-	25	4
U716-1/2	1/2	3/8	1/4	25	6
U716-5/8	5/8	1/2	3/8	25	6
U716-3/4	3/4	5/8	-	25	7
U716-7/8	7/8	3/4	1/2	25	7
U716-1	1	-	-	25	8
U716-1-1/8	1-1/8	1	-	25	8
U716-1-1/4	1-1/4	-	-	10	17
U716-1-3/8	1-3/8	1-1/4	-	10	20
U716-1-1/2	1-1/2	-	-	10	22
U716-1-5/8	1-5/8	1-1/2	-	10	23
U716-2	2	-	-	10	41
U716-2-1/8	2-1/8	-	-	10	41
U716-2-3/8	2-3/8	-	-	10	44


Standard Finish – GoldGalv®

SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Conduit and Cable Clamps****6H Series**

Conduit and Pipe Hanger



6H Series

6H-B Series
with Bolt and Hex Nut6H-TB
Threaded Series6H-T
Threaded Series**Features**




- Accommodates 1/2" through 4" EMT or rigid conduit
- Can be used for either vertical or horizontal installation
- 6HTB Series have a built-in nut so there are fewer parts to handle or drop
- Installs easily with a screwdriver

Cat. No.	Conduit Size Rigid	Conduit Size EMT	Wt./C lb
6H0	3/8" - 1/2"	1/2"	5
6H0-B	3/8" - 1/2"	1/2"	7
6H0-T	3/8" - 1/2"	1/2"	5
6H0-TB	3/8" - 1/2"	1/2"	6
6H1	3/4"	3/4"	6
6H1-B	3/4"	3/4"	7
6H1-T	3/4"	3/4"	6
6H1-TB	3/4"	3/4"	7
6H2	1"	1"	7
6H2-B	1"	1"	9
6H2-1/2	-	1-1/4"	8
6H2-1/2-B	-	1-1/4"	10
6H3-SC	1-1/4"	1-1/2"	8
6H3-B	1-1/4"	1-1/2"	10
6H3-TB	1-1/4"	1-1/2"	10
6H4	1-1/2"	-	17
6H4-B	1-1/2"	-	19
6H4-TB	1-1/2"	-	19
6H5	2"	2"	24
6H5-B	2"	2"	26
6H5-TB	2"	2"	26
6H6	2-1/2"	2-1/2"	28
6H6-B	2-1/2"	2-1/2"	30
6H7	3"	3"	36
6H7-B	3"	3"	38
6H8	3-1/2"	3-1/2"	39
6H8-B	3-1/2"	3-1/2"	41
6H9	4"	4"	44
6H9-B	4"	4"	47

Standard Finish - Electrogalvanized (no suffix)
Available in Stainless Steel 304 (SS)

Cable Tie Mounting Bases
For Framing Channel

Cat. No.	Channel Size	Maximum Tie Width Accom.	Unit Qty.	Std. Pkg.
TC5363X	1-1/2 & 1-5/8	.301	50	250

INSTALLATION

- Installs with a push and twist
- Designed for indoor or outdoor use
- Smooth design protects cable insulation
- Takes range of cable diameters



When fastening wire bundles, cables, or hoses to framing channels, you can cut costs considerably by using this mounting base. It is made of smooth, weather-resistant nylon and designed to protect cable insulation and hoses from the wear or damage that can occur with metal clamps. The mounting base may be used for both indoor or outdoor applications. It installs in the framing channel with a simple push and twist. It requires no screws, nuts or tools. The mounting base fits all 1-1/2" and 1-5/8" channels regardless of channel depth. Ty-Rap® and Ty-Fast® to be ordered separately.

Pipe Straps, Pipe Clamps and Hangers

Conduit and Cable Clamps

W716

Maple Hardwood Clamps



Paraffin impregnated maple.


Standard Finishes -
Pregalvanized (PG)
Aluminum (AL)

Hardwood paraffin imp.	Dimensions			
	Depth in.	Depth mm	Weight in.	Weight mm
W716-3/4PG	3/4	19.0	2-1/8	53.9
W716-1PG	1	25.4	2-1/8	53.9
W716-1-1/4PG	1-1/4	31.7	2-5/8	66.6
W716-1-1/2PG	1-1/2	38.1	2-5/8	66.6
W716-1-3/4PG	1-3/4	44.4	3	76.2
W716-2PG	2	50.8	3-5/8	92.0
W716-2-1/4PG	2-1/4	57.1	3-5/8	92.0
W716-2-1/2PG	2-1/2	63.5	4-5/8	117.7
W716-2-3/4PG	2-3/4	69.8	4-5/8	117.7
W716-3PG	3	76.2	4-5/8	117.7
W716-4PG	4	98.0	5-5/8	143.4

Note: Holding clamp is included with W716 maple hardwood clamps. It is not necessary to order 701 Series separately.

U861

Maple Cable Clamp



Electrogalvanized hardware included

Custom made to your needs


Step 1	Number of holes		
	i.e.	U861	1 hole
		U862	2 holes
		U863	3 holes

Step 2	Specify O.D. of cable
	i.e. 3/4" hole U861 - 0.75

Contact your Regional Sales Office for quotation.


WS716

Maple Hardwood Saddle



STD
PACK:
10

Paraffin impregnated maple.




To fasten saddle,
use 3/8" X 2" screw bolt.

Hardwood Paraffin Imp.	Dimensions			
	Depth in.	Depth mm	Width in.	Width mm
		Height in.	Height mm	
WS716-3/4	3/4	19.0	3	76.2
WS716-1	1	25.4	3	76.2
WS716-1-1/4	1-1/4	31.7	3-1/2	88.9
WS716-1-1/2	1-1/2	38.1	3-1/2	88.9
WS716-1-3/4	1-3/4	44.4	4	101.6
WS716-2	2	50.8	4	101.6
WS716-2-1/4	2-1/4	57.1	4-1/2	114.3
WS716-2-1/2	2-1/2	63.5	4-1/2	114.3
WS716-2-3/4	2-3/4	69.8	5	127
WS716-3	3	76.2	5	127
WS716-3-1/4	3-1/4	82.5	5-1/2	139.7
WS716-3-1/2	3-1/2	88.9	5-1/2	139.7
WS716-3-3/4	3-3/4	95.2	6	152.4
WS716-4	4	101	6	152.4
WS716-4-1/2	4-1/2	114.3	6-1/2	165.1
WS716-5	5	127	7	177.8
WS716-5-1/2	5-1/2	139.7	7-1/2	190.5
WS716-6	6	152.4	8	203.2
WS716-6-1/2	6-1/2	165.1	8-1/2	215.9
WS716-7	7	177.8	9	228.6

SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Conduit and Cable Clamps****AB880**

3" Porcelain Saddle


**AB881**

4" Porcelain Saddle

Cat. No.	A	Max. Cable Diam.	Wt./C lb
AB880	3	3	73
AB881	4	4-1/2	104

C755

Porcelain Cable Clamps



Cat. No.	Hole Size	A	Wt./C lb
C755-1A	3/8	1-9/16	50
C755-1B	1/2	1-9/16	50
C755-1C	5/8	1-9/16	50
C755-2	3/4	2-5/32	91
C755-2A	7/8	2-5/32	90
C755-2B	1	2-5/32	85
C755-2C	1-1/8	2-5/32	82
C755-3	1-1/4	2-5/8	114
C755-3A	1-3/8	2-5/8	110
C755-3B	1-1/2	2-5/32	105
C755-3C	1-5/8	2-5/8	102
C755-4	1-3/4	3-3/4	220
C755-4A	1-7/8	3-3/4	214
C755-4B	2	3-3/4	205
C755-4C	2-1/8	3-3/4	200
C755-5	2-1/4	4-1/4	260
C755-5A	2-3/8	4-1/4	250
C755-5B	2-1/2	4-1/4	243

Cat. No.	Hole Size	A	Wt./C lb
C755-5C	2-5/8	4-1/4	240
C755-6	2-3/4	4-3/4	250
C755-6A	2-7/8	4-3/4	240
C755-6B	3	4-3/4	230
C755-6C	3-1/8	4-3/4	220
C755-7	3-1/4	5-13/16	340
C755-7A	3-3/8	5-13/16	330
C755-7B	3-1/2	5-13/16	318
C755-7C	3-5/8	5-13/16	387
C755-8	3-3/4	6-7/8	565
C755-8A	3-7/8	6-7/8	550
C755-8B	4	6-7/8	535
C755-8C	4-1/8	6-7/8	520
C755-8D	4-1/4	6-7/8	490
C755-8E	4-3/8	6-7/8	475
C755-8F	4-1/2	6-7/8	460

Standard Finish -
GoldGalv® with bronze hardware

Also fits 1-1/2" wide channel.

For minimum order quantities contact customer service.

Pipe Straps, Pipe Clamps and Hangers


Conduit and Cable Clamps

S716

Cushioned Strip for Isolation & Vibration Applications




For use with 701 O.D. tubing and pipe clamp. To determine 701 clamp size add 1/4" to O.D. tube size to allow for the Cushioned Strip material.



1/4" markings for fast measuring and cutting.
Measurement chart is printed on back of carton. **20 feet included in each carton.**


Prevent metal to metal contact with the Cushioned Strip material. It aids in sound insulation, shock absorption and protects against corrosion, distortion and abrasion. Cushioned Strip material is designed for optimal use between -1°C and 149°C (30°F and 300°F).
Cushioned Strip material combined with the Superstrut 701 pipe strap can handle clamping assignments from 1/4" to 6."



Order 701 clamp separately.

C708U

Short Strap for Channel or Wall Mounting



Standard Finish - GoldGalv®

Example: C708U-1/2

No clearance between pipe and channel.

Pipe Size	A	B	Thickness	Width	Hole Size	Design Load lb	Wt./C lb
1/2	2-7/8	2	1/8	1-5/8	9/32	650	23
3/4	3-1/16	2-3/16	1/8	1-5/8	9/32	650	26
1	3-3/8	2-1/2	1/8	1-5/8	9/32	650	31
1-1/4	3-11/16	2-13/16	1/8	1-5/8	9/32	650	35
1-1/2	3-15/16	3-1/16	1/8	1-5/8	9/32	650	39
2	5-3/4	4-1/8	1/4	1-5/8	7/16	650	94
2-1/2	6-3/16	4-9/16	1/4	1-5/8	7/16	1000	114
3	6-13/16	5-3/16	1/4	1-5/8	7/16	1000	133
3-1/2	7-5/16	5-11/16	1/4	1-5/8	7/16	1000	152
4	7-13/16	6-3/16	1/4	1-5/8	7/16	1200	176
5	8-7/8	7-1/4	1/4	1-5/8	7/16	1200	198
6	9-15/16	8-5/16	1/4	1-5/8	7/16	1200	246

Carbon Steel

SECTION 5

Pipe Straps, Pipe Clamps and Hangers

Conduit and Cable Clamps

C711



"J" Pipe Hanger

Standard Finishes - GoldGalv®, Electrogalvanized (EG)

Complies with Specification MSS SP69, Type 5.

Hole provided for side mounting to wall as bracket.

Example: C711-1/2



Pipe Size	Rod Size	Overall Dimension					Bolt Size	G	Thickness	Width	Max. Rec. Approx.	
		B	C	D	E	F					Load lb	Wt./C lb
1/2	3/8	2-5/8	1-3/4	7/16	1-1/2	1-15/16	1/4	3-5/32	12 ga	3/4	400	18
3/4	3/8	2-7/8	1-7/8	7/16	1-11/16	2-1/8	1/4	3-1/2	12 ga	3/4	400	21
1	3/8	2-15/16	1-15/16	7/16	1-13/16	2-5/16	1/4	3-11/16	12 ga	3/4	400	22
1-1/4	3/8	3-1/4	2	7/16	2-1/16	2-5/8	1/4	4-1/8	12 ga	3/4	400	25
1-1/2	3/8	3-9/16	2-3/16	7/16	2-7/16	2-7/8	1/4	4-5/8	12 ga	3/4	400	27
2	3/8	3-11/16	2-1/8	7/16	2-9/16	3-1/16	1/4	5	12 ga	3/4	400	29
2-1/2	1/2	4-7/16	2-7/16	9/16	3-3/16	3-5/8	3/8	6	12 ga	1-1/4	500	64
3	1/2	4-13/16	2-9/16	9/16	3-1/2	4-1/16	3/8	6-21/32	12 ga	1-1/4	500	72
3-1/2	1/2	5-1/8	2-5/8	9/16	3-3/4	4-3/8	3/8	7-5/16	3/16	1-1/4	500	84
4	5/8	6-1/8	3-3/16	9/16	4-5/8	5-3/16	3/8	8-9/16	3/16	1-1/4	550	138
5	5/8	6-3/4	3-1/4	9/16	5-1/16	5-3/5	3/8	9-23/32	3/16	1-1/4	550	162
6*	3/4	7-3/4	3-9/16	9/16	5-13/16	6-5/8	3/8	11-1/4	3/16	1-3/4	600	249
8*	7/8	9-3/16	3-15/16	9/16	6-15/16	8	3/8	13-11/16	3/16	1-3/4	760	291

*Hangers 6" and over have hole instead of slot.

C727

Adjustable Ring


Standard Finish - Pregalvanized (no suffix), Stainless Steel (SS)

Carbon steel. For suspension of non-insulated pipe lines.

Complies with Specification MSS SP69, Type 10.

Example: C727-1/2

Tube Size	Rod Size	Approx. Max. Rec. Wt./C						Load
		A	B	C	Thickness	Width	lb	
1/2	3/8	3-1/8	2-5/8	1-3/8	16 ga	1	400	9
3/4	3/8	3-1/8	2-1/2	1-1/8	16 ga	1	400	9
1	3/8	3-3/8	2-5/8	1-1/8	16 ga	1	400	9
1-1/4	3/8	3-3/4	2-7/8	1-1/8	16 ga	1	400	10
1-1/2	3/8	3-7/8	2-7/8	1	16 ga	1	400	11
2	3/8	4-1/4	3	1	16 ga	1	400	12
2-1/2	1/2*	5-3/4	4-1/4	1-5/8	14 ga	1-3/16	600	28
3	1/2*	6	4-1/8	1-1/4	14 ga	1-3/16	600	30
3-1/2	1/2*	7-3/8	5-1/4	2-1/8	14 ga	1-3/16	600	34
4	5/8*	7-3/8	5	2-5/8	14 ga	1-1/4	1000	37
5	5/8**	9	6-1/8	2-1/4	12 ga	1-1/4	1250	83
6	3/4**	9-3/8	6-1/2	1-7/8	12 ga	1-1/4	1250	95



*3/8" nut is used when NFPA rod sizing is requested.

**1/2" nut is used when NFPA rod sizing is requested.

Pipe Straps, Pipe Clamps and Hangers

Pipe Hangers

C710


Adjustable Clevis Hanger

Standard Finishes - GoldGalv®, Electrogalvanized (EG)


Complies with Specification MSS SP69, Type 1.

Standard Clevis Hanger also available in Stainless Steel

Example: C710-1/2EG



Pipe Size	Size of Steel			A	B	C	D	E	F	Max. Rec. Load, lb	Wt./C lb
	Upper	Lower									
1/2	1/8x1	1/8x1	3/8	1-11/16	2-1/8	2-1/2	7/8	7/16	610	30	
3/4	1/8x1	1/8x1	3/8	1-7/8	2-7/16	2-1/2	1	1/2	610	32	
1	1/8x1	1/8x1	3/8	2-1/8	2-13/16	2-1/2	1-1/4	5/8	610	36	
1-1/4	1/8x1	1/8x1	3/8	2-9/16	3-7/16	2-1/2	1-3/4	7/8	610	42	
1-1/2	1/8x1	1/8x1	3/8	3	4	2-1/2	2-1/8	1-1/16	610	55	
2	1/8x1	1/8x1	3/8	3-11/16	4-7/8	2-1/2	2-15/16	1-5/8	610	60	
2-1/2	3/16x1-1/4	3/16x1-1/4	1/2	4-11/16	6-1/8	3	3-13/16	2	1130	115	
3	3/16x1-1/4	3/16x1-1/4	1/2	4-3/4	6-9/16	3	3-7/8	1-3/4	1130	132	
3-1/2	3/16x1-1/4	3/16x1-1/4	1/2	4-15/16	6-15/16	3	4-1/16	1-3/4	1130	156	
4	1/4x1-1/4	3/16x1-1/4	5/8	5-9/16	7-13/16	3-1/2	4-1/2	1-15/16	1430	190	
5	1/4x1-1/4	3/16x1-1/4	5/8	6-3/16	9	3-1/2	5-1/8	1-3/4	1430	240	
6	1/4x1-1/2	3/16x1-1/2	3/4	6-13/16	10-1/8	4	5-5/8	1-7/8	1940	320	
8	1/4x1-3/4	3/16x1-3/4	7/8	8-5/16	12-5/8	4-1/4	7	2-1/8	1940	500	

**CL710**

Light Duty Adjustable Clevis Hanger


Standard Finishes - GoldGalv®, Bare (B), Electrogalvanized (EG), Fiberglass (FG).

Carbon Steel

Used on non-insulated, stationary pipelines.

A lock nut above the clevis yoke is required for full rated load.

Example: CL710-3/8B



Pipe Size	Thickness of Steel			A	B	C	D	E	F	Max. Rec. Load, lb	Wt./C lb
	Upper	Lower									
3/8	16 ga x 7/8	16 ga x 7/8	3/8	1-7/8	2-3/16	2-1/2	1-1/4	9/16	150	12	
1/2	16 ga x 7/8	16 ga x 7/8	3/8	1-3/4	2-3/16	2-1/2	1-1/8	9/16	150	13	
3/4	16 ga x 7/8	16 ga x 7/8	3/8	1-7/8	2-1/4	2-1/2	1-1/4	1/2	250	15	
1	16 ga x 7/8	16 ga x 7/8	3/8	2-3/16	2-3/4	2-1/2	1-1/2	3/4	250	18	
1-1/4	16 ga x 7/8	16 ga x 7/8	3/8	2-5/8	3-3/8	2-1/2	1-3/4	1	250	20	
1-1/2	13 ga x 7/8	13 ga x 7/8	3/8	3	3-7/8	2-1/2	2-1/4	1-3/16	250	30	
2	13 ga x 7/8	13 ga x 7/8	3/8	3-9/16	4-3/4	2-1/2	2-13/16	1-5/8	250	38	
2-1/2	1/8 x 1-1/4	1/8 x 1-1/4	1/2	4	5-1/2	3	3-1/4	1-3/8	350	80	
3	1/8 x 1-1/4	1/8 x 1-1/4	1/2	4-9/16	6-1/2	3	3-9/16	1-1/2	350	89	
3-1/2	1/8 x 1-1/4	1/8 x 1-1/4	1/2	5	7	3	4-1/8	1-3/4	350	106	
4	3/16 x 1-1/4	1/8 x 1-1/4	1/2	5-1/4	7-1/2	3-1/2	4-1/4	1-7/8	400	146	



SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Pipe Hangers****M718**

Split Pipe Ring



Standard Finishes - Bare (B) or Electrogalvanized (EG)

Malleable iron.

For suspension of non-insulated, stationary pipelines.

Example: M718-3/8B

Pipe Size	A	B	Max. Rec. Load/lb	Wt./C lb
3/8	3/8	13/16	180	10
1/2	3/8	7/8	180	13
3/4	3/8	1	180	14
1	3/8	1-1/8	180	16
1-1/4	3/8	1-5/16	180	22
1-1/2	3/8	1-7/16	180	24
2	3/8	1-11/16	180	31
2-1/2	1/2	2-1/8	300	60
3	1/2	2-7/16	300	74
4	1/2	2-15/16	300	116

**C725**

Medium Pipe Clamp



Standard Finishes - GoldGalv®, Bare (B), Stainless Steel (SS), Electrogalvanized (EG)

Carbon steel. For suspension of pipelines where little or no insulation is required.

Complies with Specification MSS SP69, Type 23.

Example: C725-1/2B

Pipe Size	B	C	D	E	F	H	S	Max. Rec. Load, lb	Wt./C, lb Approx.
1/2	1	7/16	1-5/8	1	5/16	1-1/2	1/8 x 1	500	29
3/4	1-1/8	7/16	1-3/4	1-1/4	5/16	1-3/4	1/8 x 1	500	32
1	1-1/4	7/16	1-13/16	1-1/4	5/16	1-13/16	1/8 x 1	500	33
1-1/4	1-7/16	7/16	2	1-7/16	5/16	2	1/8 x 1	500	38
1-1/2	1-5/8	1/2	2-1/16	1-1/2	5/16	2-1/4	1/8 x 1	715	39
2	2-1/8	9/16	3-1/8	2-1/4	1/2	3	1/4 x 1	1040	117
2-1/2	2-5/16	9/16	3-5/16	2-1/2	1/2	3-1/4	1/4 x 1	1040	128
3	2-3/4	9/16	3-3/4	2-3/4	1/2	3-5/8	1/4 x 1	1040	140
3-1/2	3-7/8	5/8	3-3/4	3	1/2	3-7/8	1/4 x 1	1040	145
4	3-5/16	3/4	4-1/4	3-5/16	5/8	4-1/4	1/4 x 1-1/4	1040	238
6	4-7/8	7/8	5-7/8	5	3/4	5-3/4	3/8 x 1-1/2	1615	542
8	6	1	7	6-1/8	3/4	6-7/8	3/8 x 1-1/2	1615	651
10	7-5/16	1	8-9/16	7-7/16	7/8	8-7/16	1/2 x 2	2490	1360
12	8-1/4	1	9-9/16	8-7/16	7/8	9-3/8	1/2 x 2	2490	1605



Based on the allowable stresses shown in ANSI Code for pressure piping.

For sizes 14 to 24, contact Customer Service.

Pipe Straps, Pipe Clamps and Hangers

Pipe Hangers

C720

Riser Clamp


Standard Finishes - GoldGalv®, Bare (B), Stainless Steel (SS)

Available in sizes 1/2" through 10".

Complies with Specification MSS SP69, Type 8.

Example: C720-1 1/2B

Pipe Size	A	Thickness	Width	Bolt	Max. Rec. Load, lb	Wt./Ea. Approx.
1/2	9-1/8	3/16	1	3/8 x 1-1/2	220	1.01
3/4	9-1/4	3/16	1	3/8 x 1-1/2	220	1.06
1	9-5/8	3/16	1	3/8 x 1-1/2	220	1.07
1-1/4	9-7/8	1/4	1	3/8 x 1-1/2	250	1.12
1-1/2	10	1/4	1	3/8 x 1-1/2	250	1.20
2	10-1/2	1/4	1	3/8 x 1-1/2	300	1.25
2-1/2	11-1/16	1/4	1	3/8 x 1-1/2	400	1.67
3	11-13/16	1/4	1	3/8 x 1-1/2	500	1.81
3-1/2	13	1/4	1	1/2 x 1-1/2	600	2.12
4	13-1/2	1/4	1	1/2 x 1-1/2	750	2.22
5	14	1/4	1-1/2	1/2 x 1-3/4	1500	3.44
6	15-3/16	1/4	1-1/2	1/2 x 1-3/4	1600	3.65
8	19	3/8	1-1/2	5/8 x 2-1/2	2500	7.24



C726

Double Bolt Pipe Clamp

Standard Finish - Bare (B)


Carbon Steel. For the suspension of insulated pipelines.

Normally used with weldless eye nut.

Example: C726-1/2B



Pipe Size	B	C	D	E	F	H	S	Max. Rec. Load, lb	Approx. Wt. /C
3/4	1-1/16	5/8	3-3/16	2-1/2	3/8	1-11/16	3/16 x 1	950	66
1	1-1/2	5/8	3-3/4	2-1/2	3/8	2-1/16	3/16 x 1	950	69
1-1/4	1-1/2	3/4	3-11/16	2-7/8	3/8	2-1/4	3/16 x 1	950	75
1-1/2	1-13/16	1-1/16	4-7/8	3-3/4	5/8	2-13/16	1/4 x 1-1/4	1545	181
2	2-1/4	1-1/16	5-11/16	4-11/16	5/8	3-3/16	1/4 x 1-1/4	1545	200
2-1/2	2-5/8	1-1/16	6-1/2	5-3/8	5/8	3-1/2	1/4 x 1-1/4	1545	232
3	2-3/4	1-1/16	6-7/8	6	5/8	3-3/4	1/4 x 1-1/4	1545	258
3-1/2	3	1-1/16	7-1/16	6-3/16	5/8	4	1/4 x 1-1/4	1545	264
4	3-3/8	1-1/16	7-5/8	6-1/2	3/4	4-1/2	3/8 x 2	2500	750
5	3-15/16	1-1/16	8-1/8	7	3/4	5	3/8 x 2	2500	813
6	4-3/4	1-7/16	9-15/16	8-9/16	1	6-1/8	3/8 x 2-1/2	2865	1311
8	5-3/4	1-7/16	10-15/16	9-9/16	1	7-1/8	3/8 x 2-1/2	2865	1467




SECTION 5**Pipe Straps, Pipe Clamps and Hangers****Seismic Bracing**

Consult Superstrut® seismic Hanger Bulletin (GM141) for additional information

C749N


Seismic Brace

Standard Finish - GoldGalv®

1650 lb. load
safety factor 3
Wt./C 61 lb

C749N-5/8


Seismic Brace

Standard Finish - GoldGalv®

1650 lb. load
safety factor 3
Wt./C 56 lb

C749N-7/8


Seismic Brace

Standard Finish - GoldGalv®

1650 lb. load
safety factor 3
Wt./C 74 lb

C749N-1 1/8

Seismic Brace

Standard Finish - GoldGalv®

1650 lb. load
safety factor 3
Wt./C 72 lb

ES142*Standard Finish - GoldGalv®*

Cat. No.	Bolt Dia.	Wt./C lb
ES-142-1/2 x 1-1/2	1/2	21












Seismic bracing rod
stiffener connector.
Wt./C 21 lb

All braces have plastisol coating on the flat member.

Plastisol insulates against vibration noise transmission and eliminates rattle at the connection points.

SECTION 5**Hanger Accessories****Hanger Accessories**



Other products available. Contact your Regional office.

C704A Offset J-Hook  Sizes 1/2" thru 3" IPS	M732H I-Beam w/Eye Nut  MSS SP69 Type 28	M732 / M732 Ext I-Beam Clamp w/Swing Nut  Sizes 3/8" thru 7/8" Rod MSS SP69 Type 30	C736 Light Welded Steel Bracket  Max. Load 750 Lb MSS SP69 Type 31	C739M Medium Welded Steel Bracket  Max. Load 1500 Lb MSS SP69 Type 32
C739H Heavy Welded Steel Bracket  Max. Load 3000 Lb MSS SP69 Type 33	M750 Side Beam Bracket  Sizes 3/8" thru 7/8" Rod MSS SP69 Type 34	C785A Pipe Stanchion Saddle  Sizes 4" thru 36" IPS MSS SP69 Type 37	C786 Adj. Pipe Saddle Support  Sizes 2-1/2" thru 36" IPS MSS SP69 Type 38	C789 Steel Pipe Covering Protection Saddle  MSS SP69 Type 39
C790 Insulation Protection Shield for PVC coated pipe lines and insulated copper tubing  Sizes 3/4" thru 12" IPS MSS SP69 Type 40	RC729A Single Pipe Roll  Sizes 1" thru 24" IPS MSS SP69 Type 41	C729 Adj. Roller Hanger  Sizes 1" thru 20" IPS MSS SP69 Type 43	S730C Pipe Roll + Base  MSS SP69 Type 44	S730D Adj. Pipe Roll & Base  MSS SP69 Type 46
C769 Top I-Beam Clamp  Sizes 3/4" thru 7/8" Rod MSS SP69 Type 25	C755 T / C757 T Center I-Beam Clamp  MSS SP69 Type 21	C780 Weld attachment as shown or inverted less bolt  MSS SP69 Type 22	M778 Top Beam C-Clamp  Sizes 3/8" thru 3/4" Rod MSS SP69 Type 19	M777 Junior Top Beam C-Clamp  Sizes 3/8" thru 1/2" Rod MSS SP69 Type 18



SECTION 6
SURFACE RACEWAY AND
LIGHTING SYSTEMS

Thomas&Betts



Material

Superstrut® electrical raceway, fixture hanging channel, closure strip and accessories are manufactured from hot rolled strip steel. Standard finish for the accessories is GoldGalv®.

Design Data

Deflections at various hanger rod spacings for raceway channels based on 40 to 45 lb per fixture.

Deflection

Channel	at 10 ft	at 12 ft	at 14 ft
A1200	1/4"	1/2"	3/4"
C1200	3/8"	3/4"	*
A1400	3/8"	3/4"	*

Deflection

Channel	at 6 ft	at 7 ft	at 9 ft
B1200	3/8"	9/16"	5/8"
B1400	1"	1/2"	*

*Not recommended for this spacing.

Electrical Raceway

Superstrut channel together with snap-in closure strip is listed by Underwriters Laboratories as a surface metal raceway. Other accessories listed by Underwriters Laboratories are identified on the drawings.

MAXIMUM NUMBER OF WIRES

Wire Size AWG	Raceway							
	With or without KO		B1200		C1200		E1200 H1200	
	A	B	A	B	A	B	A	B
14	6	10	4	6	5	10	6	10
12	6	10	3	6	4	10	6	10
10	5	8			4	6	5	8
8	4	6			3	4	4	6
6	2	3			2	2	2	3

COLUMN A: Suitable for number of wires indicated when used as a raceway. Also suitable for number of wires indicated when installed to support and supply electrical fixtures when raceway wiring is suitable for not less than 75°C.

By providing clearance between fixture and raceway of not less than 1/2", where suitable for 60°C may be used.


COLUMN B: Suitable for number of wires indicated when used as a raceway. Also suitable for number of wires indicated when installed to support electrical fixtures when clearance of not less than 1/8" is provided between raceway and fixture and when wiring is suitable for 75°C.

Applicable Channels

A1200	B1200
A1200-KO	B1400
A1400	C1200
A1400-KO	E1200
	H1200

SECTION 6**Surface Raceway and Lighting Systems****Fixture Fittings****802**

Raceway Joiner With Reinforcing Plate




Furnished complete with nuts.

Cat. No.	For Channel	Wt./C
	lb	
A802EG	A Series	158
B802EG	B Series	112
E802EG	E Series	170
H802	H Series	182

822

Raceway Joiner & Seal




Furnished complete with 1/4" x 5/8" machine screws and AB100-1/4 nuts.


Cat. No.	A	For Channel	Wt./C
	lb		
A822	1-11/16	A Series	75
B822	7/8	B Series	56

A213

Inside Joiner

For A1200 series channel
Only available in GoldGalv® finish**805**


End Cap With Knockout

KO for 1/2" conduit.
Furnished complete with 1/4" x 5/8" flat head machine screw and AB100-1/4 nut.

Cat. No.	For Channel	Wt./C
	lb	
A805EG	A Series	21
H805EG	H Series	31

809

Tapped End Cap



12 ga. steel. For 3/4" or 1" conduit. Furnished complete with 1/4" x 5/8" flat head machine screw and AB100-1/4 nut.

Cat. No.	For Channel	Wt./C
	lb	
A809-3/4EG	A Series	2
E809-3/4EG	E Series	26

A853

Channel Hanger




Use hanger rod 3/8" or 1/2". Use with A, AR, B, BR or C series single channel.

Wt./C 25 lb

A853L

Channel Hanger - Long




Long type for all series channel.

Wt./C 48 lb

A854


Channel Hanger

Illustration showing A854 with nut and bolt furnished to attach to fluorescent fixture.
Use with A, B, C or D series channel.

Wt./C 34 lb

A854L


Channel Hanger - Long

Illustration showing A854L with nut and bolt furnished to attach to fluorescent fixture.
Use with E and H series channel as well as A, B, C or D.

Wt./C 51 lb

Surface Raceway and Lighting Systems**Fixture Fittings****AB844PGC**

Steel Closure Strip



LISTED

AB844PC

Plastic Closure Strip Colour: Gold


AB844PCGY

Plastic Closure Strip Colour: Grey

- When used as a raceway is channel is normally installed with the slot up. After wiring has been completed the closure strip is installed.
- For all channels.
- Standard length: 10 ft

AB803

Cast Conduit Connector




LISTED

To connect 1/2" or 3/4" conduit to raceway channel. Furnished complete with stud nuts and hex nuts. Part has removable bushing to increase size from 1/2" to 3/4".

Wt./C 60 lb

AB815

Swing Connector




Nuts and bolts to clamp to channel is included. For 1/2" or 3/4" conduit.

Wt./C 95 lb

AB885

15° Swivel




Nuts and bolts to clamp to channel included. For 1/2" or 3/4" conduit.

Wt./C 25 lb

AB867

Spacer




For use with AB866
wiring stud nuts.

Wt./C 24 lb

AB866

Wiring Stud Nut




1/2" Pipe thread

Wt./C 21 lb

811

Stud Nut



Cat. No.	For Channel	Wt./C
811-1STR	1/4 x 1	8
811-2STR	1/4 x 1-1/4	9

812

Stud Nut




For attaching fixture to slot down channel or to slot up knockouts. Specify length.
Hex nut included.

Cat. No.	For Channel	Wt./C
812-1EG	1/4 x 1	6













AB868

Fiber Retainer for Cables Until Closure Strip is Installed



Wt./C 3 lb

SECTION 6**Surface Raceway and Lighting Systems****Kindorf® Channel Boxes and Receptacles**



G2000  Finish - GoldGalv® Wt./C 110 lb	G2001  Finish - GoldGalv® Wt./C 120 lb	G2002  Finish - GoldGalv® Wt./C 120 lb
G2003  Finish - GoldGalv® Wt./C 130 lb	G2004  Finish - GoldGalv® Wt./C 140 lb	G1038 Duplex Outlet  Complete unit including housing, standard DUPLEX 3-wire, 15 Amp., 125 volt, ground receptacle and cover plate. Finish - GoldGalv® Wt./C 55 lb
G1038A Single Outlet  Finish - GoldGalv® Wt./C 50 lb	G1038D Raceway Outlet  Finish - GoldGalv® Wt./C 60 lb	G1038E Raceway Outlet  Complete unit including housing, single, 3-wire, 15 amp. 277 volt-twistlock receptacle and cover plate. Finish - GoldGalv® Wt./C 50 lb
G1038B Housing Only  Finish - GoldGalv® Wt./C 25 lb	G1038C Duplex Cover Plate  Finish - GoldGalv® Wt./C 12 lb	G1038CA Single Cover Plate  Size of opening: 1.391 diameter Finish - GoldGalv® Wt./C 14 lb
G1038CX Blank Cover Plate  Finish - GoldGalv® Wt./C 15 lb		

Surface Raceway and Lighting Systems

Kindorf® Fixture Accessories

G1017

Mercury Vapor Hanger




Used with Channel	Depth in.	Wt./C lb
A-1200	4-1/4"	76

Finish - GoldGalv®

To support high or low bay mercury vapor or heavy incandescent fixtures from raceway channels. Permits plug-in connections with G-1038 raceway outlets.


G972HB1/2

Steel Fixture Hanger Adapter


Finish - GoldGalv®


The hanger adapter securely mounts the fixture hanger or box to the channel through the 1/2" KO in the base. No special tools are needed for installation of fittings and fixtures. Superstrut® channels, with 1/2" KO's every 6", hangs and feeds the fixtures thereby simplifying installation.



Wt./C 17 lb



Electrical Applications




SECTION 6**Surface Raceway and Lighting Systems****Electrical Applications**

Surface Raceway and Lighting Systems**SECTION 6****Electrical Applications**



SECTION 7
RIGHT ANGLE SLOTTED
METAL FRAMING


Thomas & Betts

Right Angle Slotted Metal Framing**SECTION 7****Create the support framing you need**

Right Angle Metal Framing is manufactured from commercial quality steel in three different sizes. The small sizes are 14 ga. steel, the larger is 12 ga. steel. With this offering, an endless variety of metal framing requirements can be met, from lightweight supporting needs to larger shelving for inventory storage.

One of the legs on all sizes is 1-5/8" wide, while the other is either 1-5/8", 2-3/8" or 3-1/8" long. Depending on the frame requirements, a single size can be utilized throughout, or the sizes can be interchanged to get the most efficient usage from the material.

This section will serve as a guide to plan and build your structure.


**Installation time is reduced - inventory space is minimal**

Scribe marks are placed every 3/4" which saves planning, layout and cutting time and ensures accuracy. The exclusive slot and hole pattern, repeated every 3", is scientifically designed for ease of assembly and rigidity. No welding is necessary, no holes to drill. A 9/16" wrench is the only tool required for assembly. The proper nuts and bolts are included with the material to ensure fast and easy erection.

Right Angle Metal Framing is packaged in 10' and 12' lengths to minimize cut offs and ensure maximum use of material.

120 feet, 10, 12 foot lengths of Right Angle Metal Framing take up the same amount of space as one 2x4. A standard package includes 5 pieces to a bundle, significantly reducing handling and storage space.


The importance of cutting Right Angle easily, quickly and accurately is the key to time saving assembly. The portable cutter provides these advantages and makes layout and erection of any structure a "light-work" job.

**Finish is designed for long lasting durability**

The standard GoldGalv® hardware finish is applied to all Right Angle Metal Framing after rolling and punching of the holes. This provides you with a number of benefits. First, raw ends resulting from cuts will be protected by the sacrificial quality of zinc. Second, the edges of all holes are protected against formation of rust, to provide a call back free installation. Third, the electrogalvanizing provides an excellent bonding surface for paint if desired for aesthetic reasons.




Note: Product is also available in pregalvanized (PG) sections.

Flexibility**Simplicity****Economy**

SECTION 7**Right Angle Slotted Metal Framing**RA-160
14 Gauge

Cat. No.	Length ft	No. of ft./per Pkg.
RA-160-10	10	50
RA-160-12	12	60
RA-225-10	10	50
RA-225-12	12	60
RA-300-10	10	50
RA-300-12	12	60



Each package includes 36 nuts and bolts.

RA-225
14 GaugeRA-300
12 Gauge


EXTRA NUTS AND BOLTS

Cat. No.	Package 100 Sets	Std. Ctn.
RA-BN-5/8	2-3/8" - 16 x 1-5/8"	100
RA-BN-3/4	2-3/8" - 16 x 3/4"	100

Use with RA-160 & RA-225
Use with RA-300

RA-GP
Gusset Plate
For extra rigid assemblyRA-C
Portable Cutter

Cat. No.	Package	Std. Ctn.
RA-GP	25	100
RA-RC	2	2
RA-SC	2	2
RA-C	1	1



RA-RC RA-SC

Rigid & Swivel Casters
Hard rubber composition 3-1/2" dia. with
load rating of 225 lb per wheel.

Superstrut

Thomas&Betts




SECTION 8
ENGINEERING DATA AND
SPECIFICATIONS

Thomas & Betts

Engineering Data & Specifications

SECTION 8

**Design Data –
Metal Framing Channel**
**TABLE 1
Properties for Design**
Elements of Sections**Single Channels****Double Channels**
**Nominal Thickness
(inches)**

12 ga = .105

14 ga = .075

16 ga = .060

Legend	
I	- Moment of inertia
S	- Section Modulus
r	- Radius of Gyration
Z	- Nominal Axis
A	- Area

SECTION MEMBER	WT. lb/ft	H in.	W in.	A in. ²	X-X AXIS			Y-Y AXIS		
					I in. ⁴	S in. ³	r in.	I in. ⁴	S in. ³	r in.
SINGLE CHANNEL										
A1200	1.90	1.625	1.625	.557	.192	.212	.587	.719	.237	.292 .652
B1200	1.28	.813	1.625	.381	.031	.063	.283	.331	.137	.168 .600
C1200	1.70	1.375	1.625	.500	.121	.155	.492	.595	.205	.252 .640
D1200	1.44	1.000	1.625	.424	.053	.092	.356	.403	.159	.196 .616
E1200	2.47	2.438	1.625	.726	.529	.399	.853	1.112	.335	.413 .679
H1200	3.05	3.250	1.625	.897	1.100	.6351	1.107	1.507	.436	.536 .697
A1400	1.40	1.625	1.625	.401	.134	.146	.577	.707	.184	.226 .677
B1400	.97	.813	1.625	.280	.024	.051	.295	.338	.103	.127 .607
DOUBLE CHANNEL										
A1202	3.80	3.250	1.625	1.114	.948	.583	.992	1.625	.474	.584 .652
B1202	2.56	1.626	1.625	.762	.147	.181	.439	.813	.274	.337 .600
C1202	3.40	2.750	1.625	1.000	.595	.433	.772	1.375	.409	.504 .640
D1202	2.88	2.000	1.625	.847	.257	.257	.552	1.090	.319	.393 .616
E1202	4.94	4.876	1.625	1.450	2.854	1.1711	1.402	2.438	.672	.827 .680
H1202	6.10	6.500	1.625	1.794	6.273	1.9301	1.870	3.250	.871	1.072 .697
A1402	2.80	3.250	1.625	.801	.668	.411	.913	1.625	.367	.452 .677
B1402	1.94	1.626	1.625	.560	.112	.138	.447	.813	.206	.254 .607

TABLE 2**Maximum Pullout and Slip Loads for Steel Channel and Channel Nuts**

Channel Nut Size / Thread	Channel	Pull-Out Strength		Slip Resistance		Torque	
		All Series	lb	kN	lb	kN	ft lb
1/4 - 20	A1200	600	2.7	300	1.3	6	8
5/16 - 18	B1200	800	3.6	500	2.2	11	15
3/8 - 16	C1200	1000	4.4	800	3.6	19	25
1/2 - 14	D1200	2000	8.9	1500	6.7	50	70
5/8 - 11	E1200	2500	11.1	1500	6.7	100	135
3/4 - 10	H1200	2500	11.1	1700	7.6	125	170
1/4 - 20	A1400	600	2.7	300	1.3	6	8
5/16 - 18		800	3.6	400	1.8	11	15
3/8 - 16		1000	4.4	750	3.3	19	25
1/2 - 14		1400	6.2	1000	4.4	50	70
1/4 - 20	AR1600	600	2.7	300	1.3	6	8
5/16 - 18		800	3.6	400	1.8	11	15
3/8 - 16		1000	4.4	750	3.3	19	25
1/2 - 14		1000	4.4	1000	4.4	50	70

For aluminum channel the pull out load is calculated by multiplying the appropriate data by 50%. For slip resistance multiply by 75%.

Maximum Pullout and Slip Loads for Fiber Glass Channel and Channel Nuts

Channel Nut Size / Thread	Channel	Pull-Out Strength		Slip Resistance		Torque		
		All Series	lb	kN	lb	kN	ft lb	N-m
1/4 - 20	-	-	-	-	-	-	-	-
5/16 - 18	-	-	-	-	-	-	-	-
3/8 - 16	A1200	300	1.3	150	0.6	200	22.6	
1/2 - 13	D1200	300	1.3	150	0.6	200	22.6	

Design Data – Metal Framing Channel**TABLE 3**

Design loads for channel used as beam or column

BEAM LOADS

Table 3 contains simple beam, uniformly-distributed loads calculated at 25,000 psi material stress. Beam loads are based on channel being loaded across the x-x axis. Loads are also listed at reduced deflections for long spans.

Maximum loads @ 25,000 psi stress

Maximum allowable deflections and maximum uniform loads for all spans @ 25,000 psi material stress.

Reduced load for all 1/180 Span Deflection

For moderate deflections on the longer spans, reduced loads are listed which will produce a deflection equal to 1/180 of the span. When maximum loads do not induce deflections exceeding $1/180 \times$ the span length reduced loads are not required.

Reduced load for 1/360 Span Deflection

For very slight deflections on the longer spans, reduced loads are listed which will produce a deflection equal to 1/360 of the span. When maximum loads do not induce deflections exceeding $1/360 \times$ the span length reduced loads are not required.

CONCENTRATED LOADS

To obtain values for concentrated loads from Table 3, multiply uniform load by 0.5 and deflection by 1.25.

Slotted, Punched, or KO Channel

Reduce load rating 5%.

Long span deep beams

Support in a manner to prevent rotation at supports and tie between supports to prevent twist.

COLUMN LOADS

Allowable column loads given are for uniform axial loading with pinned ends. For eccentric loading or other end conditions reduce allowable loads according to standard engineering practice.

DYNAMIC LOADS

Allowable dynamic loads may be calculated by dividing the static loads shown in Table 3, by 2.08.

Maximum beam and column loading for special materials is multiplied with the following factors:

Channel Type	Beam Load	Column Load
Stainless Steel	1	1
Aluminum	0.33	0.33

Warning

Load tables, charts and design criteria provided in this catalogue are intended as guides only. Selection of proper product, installation intervals, erection, and placement are the responsibility of the user.

Pipe hanger products when improperly used as tools of erection have occasionally failed. The user is cautioned to use the product only as it was intended to avoid an accident.

Thomas & Betts reserves the right to change material and finish specifications without notice, to improve its products.

Engineering Data & Specifications

SECTION 8

Design Data – Metal Framing Channel

TABLE 3 (cont'd.)

SINGLE CHANNEL							DOUBLE CHANNEL (Single Channels welded back-to-back)							
Cat. No.	Depth	Ga.	Maximum	1/180	1/360	Col.	Maximum	1/180	1/360	Col.				
			Uniform Load	Defl.	Load Defl.		Span	Defl.	Span					
12" BEAM OR COLUMN														
A1200	1-5/8	12	3,534	.014	.067	.033	10,533	A1202	3-1/4	12	.008	.067	.033 21,177	
B1200	13/16	12	1,050	.026	.067	.033	6,683	B1202	1-5/8	12	3,016	.016	.067 .033 14,110	
C1200	1-3/8	12	2,584	.016	.067	.033	9,345	C1202	2-3/4	12	.010	.067	.033 18,990	
D1200	1	12	1,538	.022	.067	.033	8,670	D1202	2	12	.012	.067	.033 18,312	
E1200	2-7/16	12	6,650	.010	.067	.033	13,830	E1202	4-7/8	12	.005	.067	.033 27,623	
H1200	3-1/4	12	10,583	.008	.067	.033	17,106	H1202	6-1/2	12	.004	.067	.033 34,210	
A1400	1-5/8	14	2,434	.015	.067	.033	7,575	A1402	3-1/4	14	.008	.067	.033 15,250	
B1400	13/16	14	850	.028	.067	.033	4,950	B1402	1-5/8	14	2,300	.016	.067 .033 10,390	
18" BEAM OR COLUMN														
A1200	1-5/8	12	2,355	.033	.100	.050	10,2100	A1202	3-1/4	12	.018	.100	.050 20,609	
B1200	13/16	12	700	.059	.100	.050	6,058	B1202	1-5/8	12	2,011	.036	.100 .050 13,440	
C1200	1-3/8	12	1,723	.038	.100	.050	8,970	C1202	2-3/4	12	4,811	.021	.100 .050 18,470	
D1200	1	12	1,025	.052	.100	.050	7,930	D1202	2	12	.028	.100	.050 17,942	
E1200	2-7/16	12	4,434	.023	.100	.050	13,482	E1202	4-7/8	12	.013	.100	.050 16,926	
H1200	3-1/4	12	7,055	.016	.100	.050	16,693	H1202	6-1/2	12	.009	.100	.050 33,390	
A1400	1-5/8	14	1,623	.031	.100	.050	7,334	A1402	3-1/4	14	.018	.100	.050 14,867	
B1400	13/16	14	566	.063	.100	453	.050	4,150	B1402	1-5/8	14	1,534	.036	.100 .050 9,910
24" BEAM OR COLUMN														
A1200	1-5/8	12	1,766	.058	.133	.067	9,842	A1202	3-1/4	12	4,858	.031	.133 .067 19,974	
B1200	13/16	12	525	.105	.133	333	.067	5,315	B1202	1-5/8	12	1,509	.064	.133 .067 12,670
C1200	1-3/8	12	1,291	.066	.133	.067	8,545	C1202	2-3/4	12	3,609	.038	.133 .067 17,890	
D1200	1	12	769	.087	.133	490	.067	7,050	D1202	2	12	2,680	.042	.133 .067 17,160
E1200	2-7/16	12	3,325	.039	.133	.067	13,082	E1202	4-7/8	12	.021	.133	.067 26,143	
H1200	3-1/4	12	5,291	.030	.133	.067	16,277	H1202	6-1/2	12	.016	.133	.067 32,435	
A1400	1-5/8	14	1,216	.056	.133	.067	7,058	A1402	3-1/4	14	3,425	.033	.133 .067 14,426	
B1400	13/16	14	425	.110	.133	258	.067	4,000	B1402	1-5/8	14	1,150	.064	.133 .067 9,350
30" BEAM OR COLUMN														
A1200	1-5/8	12	1,414	.089	.167	.083	9,419	A1202	3-1/4	12	3,886	.049	.167 .083 19,261	
B1200	13/16	12	420	.164	.167	266	.083	4,465	B1202	1-5/8	12	1,206	.100	.167 .083 11,803
C1200	1-3/8	12	1,034	.104	.167	1,040	.083	8,060	C1202	2-3/4	12	2,886	.059	.167 .083 17,230
D1200	1	12	.615	.129	.167	389	.083	6,650	D1202	2	12	2,128	.084	.167 .083 16,480
E1200	2-7/16	12	2,660	.063	.167	.083	12,640	E1202	4-7/8	12	7,806	.034	.167 .083 25,259	
H1200	3-1/4	12	4,234	.046	.167	.083	15,698	H1202	6-1/2	12	.025	.167	.083 31,395	
A1400	1-5/8	14	974	.088	.167	.083	6,753	A1402	3-1/4	14	2,740	.050	.167 .083 13,937	
B1400	13/16	14	340	.172	.167	165	.083	3,420	B1402	1-5/8	14	920	.100	.167 .083 8,730

When no numbers are shown, use the maximum uniform load.
Deflections are given in inches; loads in lb

Design Data – Metal Framing Channel
TABLE 3 (cont'd.)

SINGLE CHANNEL								DOUBLE CHANNEL (Single Channels welded back-to-back)										
Cat. No.	Depth	Ga.	Maximum	1/180	1/360	Col.	Load	Maximum	1/180	1/360	Col.	Load	Load Defl.	Span	Span			
			Uniform Load	Defl.	Load Defl.			Span	Span	Load Defl.				Span	Load Defl.			
36" BEAM OR COLUMN																		
A1200	1-5/8	12	1,178	.129	.200	917	.100	8,962	A1202	3-1/4	12	3,239	.071	.200	.100	18,470		
B1200	13/16	12	350	.236	.200	148	.100	3,498	B1202	1-5/8	12	1,005	.144	.200	702	.100	10,840	
C1200	1-3/8	12	861	.149	.200	578	.100	7,525	C1202	2-3/4	12	2,400	.085	.200	.100	16,500		
D1200	1	12	513	.198	.200	217	.100	4,335	D1202	2	12	1,428	.114	.200	1248	.100	15,057	
E1200	2-7/16	12	2,216	.088	.200	.100		12,160	E1202	4-7/8	12	6,505	.048	.200	.100	24,316		
H1200	3-1/4	12	3,528	.068	.200	.100		15,132	H1202	6-1/2	12	.036		.200	.100	30,265		
A1400	1-5/8	14	811	.126	.200	640	.100	6,416	A1402	3-1/4	14	2,284	.071	.200	.100	13,416		
B1400	13/16	14	284	.248	.200	115	.100	2,755	B1402	1-5/8	14	766	.144	.200	535	.100	8,050	
42" BEAM OR COLUMN																		
A1200	1-5/8	12	1,010	.175	.233	674	.117	8,466	A1202	3-1/4	12	2,776	.098	.233	.117	17,635		
B1200	13/16	12	300	.323	217	.233	109	.117	2,579	B1202	1-5/8	12	863	.195	.233	516	.117	9,790
C1200	1-3/8	12	738	.203	.233	425	.117	6,945	C1202	2-3/4	12	2,063	.115	.233	.117	15,730		
D1200	1	12	440	.264	319	.233	160	.117	3,280	D1202	2	12	1,224	.166	.233	1069	.117	13,042
E1200	2-7/16	12	1,900	.120	.233	.117		11,698	E1202	4-7/8	12	5,576	.065	.233	.117	23,272		
H1200	3-1/4	12	3,024	.091	.233	.117		14,514	H1202	6-1/2	12	.049		.233	.117	29,025		
A1400	1-5/8	14	695	.160	.233	470	.117	6,051	A1402	3-1/4	14	1,958	.225	.233	.117	12,832		
B1400	13/16	14	243	.336	168	.233	84	.117	2,060	B1402	1-5/8	14	658	.195	.233	393	.117	7,300
48" BEAM OR COLUMN																		
A1200	1-5/8	12	884	.228	.267	516	.133	7,943	A1202	3-1/4	12	2,429	.128	.267	.133	16,730		
B1200	13/16	12	263	.420	167	.267	83	.133	1,981	B1202	1-5/8	12	754	.255	.267	395	.133	8,640
C1200	1-3/8	12	646	.265	.267	325	.133	6,325	C1202	2-3/4	12	1,804	.151	.267	.133	14,890		
D1200	1	12	384	.352	244	.267	122	.133	2,439	D1202	2	12	1,071	.203	.267	702	.133	11,387
E1200	2-7/16	12	1,663	.156	.267	.133		11,092	E1202	4-7/8	12	4,879	.085	.267	.133	22,170		
H1200	3-1/4	12	2,646	.120	.267	.133		13,850	H1202	6-1/2	12	.064		.267	.133	27,700		
A1400	1-5/8	14	609	.120	.267	360	.133	5,658	A1402	3-1/4	14	1,713	.128	.267	.133	12,223		
B1400	13/16	14	213	.440	129	.267	64	.133	1,580	B1402	1-5/8	14	575	.255	.267	301	.133	6,480
54" BEAM OR COLUMN																		
A1200	1-5/8	12	785	.289	.300	408	.150	7,369	A1202	3-1/4	12	2,159	.161	.300	.150	15,763		
B1200	13/16	12	234	.533	132	.300	66	.150	1,555	B1202	1-5/8	12	670	.323	.300	312	.150	7,405
C1200	1-3/8	12	574	.335	.300	257	.150	5,650	C1202	2-3/4	12	1,604	.190	.300	1,263	.150	13,990	
D1200	1	12	341	.466	193	.300	96	.150	2,012	D1202	2	12	952	.266	.300	624	.150	10,391
E1200	2-7/16	12	1,478	.198	.300	1,123	.150	10,505	E1202	4-7/8	12	4,338	.108	.300	.150	20,980		
H1200	3-1/4	12	2,351	.151	.300	.150		13,150	H1202	6-1/2	12	7,149	.081	.300	.150	16,280		
A1400	1-5/8	14	541	.286	.300	284	.150	5,241	A1402	3-1/4	14	1,523	.161	.300	.150	11,566		
B1400	13/16	14	189	.556	102	.300	51	.150	1,250	B1402	1-5/8	14	511	.323	.300	238	.150	5,580

When no numbers are shown, use the maximum uniform load.
Deflections are given in inches; loads in lb

Engineering Data & Specifications

Design Data – Metal Framing Channel

TABLE 3 (cont'd.)

SINGLE CHANNEL							DOUBLE CHANNEL (Single Channels welded back-to-back)												
Cat. No.	Depth	Ga.	Maximum	1/180	1/360	Col.	Maximum	1/180	1/360	Col.	Load	Load	Load						
			Uniform Load	Defl.	Load Defl.		Span	Span	Load Defl.										
60" BEAM OR COLUMN																			
A1200	1-5/8	12	706	.358	.333	6,762	A1202	3-1/4	12	1,944	.199	.333	.167	14,738					
B1200	13/16	12	210	.658	107	.333	53	.167	-	B1202	1-5/8	12	604	.398	.333	253	.167	6,100	
C1200	1-3/8	12	516	.414	.333	208	.167	4,920	C1202	2-3/4	12	1,444	.235	.333	1,023	.167	13,050		
D1200	1	12	308	.550	157	.333	78	.167	1,561	D1202	2	12	257	.318	.333	449	.167	7,531	
E1200	2-7/16	12	1,330	.244	.333	909	.167	9,874	E1202	4-7/8	12	3,904	.133	.333	.167	19,734			
H1200	3-1/4	12	2,116	.186	.333	.167	12,406	H1202	6-1/2	12	6,434	.100	.333	.167	24,810				
A1400	1-5/8	14	486	.353	.333	231	.167	4,792	A1402	3-1/4	14	1,370	.199	.333	.167	10,878			
B1400	13/16	14	170	.687	82	.333	41	.167	-	B1402	1-5/8	14	460	.399	.333	193	.167	4,640	
66" BEAM OR COLUMN																			
A1200	1-5/8	12	643	.432	.367	273	.183	6,127	A1202	3-1/4	12	1,766	.240	.367	1,347	.183	13,646		
B1200	13/16	12	191	.795	88	.367	44	.183	-	B1202	1-5/8	12	549	.481	418	.367	209	.183	5,055
C1200	1-3/8	12	470	.501	344	.367	172	.183	4,145	C1202	2-3/4	12	1,313	.285	.367	846	.183	12,030	
D1200	1	12	280	.675	129	.367	65	.183	1,280	D1202	2	12	779	.377	593	.367	360	.183	6,581
E1200	2-7/16	12	1,210	.295	.367	753	.183	9,211	E1202	4-7/8	12	3,549	.180	.367	.183	18,415			
H1200	3-1/4	12	1,924	.226	.367	.183	11,616	H1202	6-1/2	12	5,849	.120	.367	.183	23,230				
A1400	1-5/8	14	443	.426	.367	190	.183	4,311	A1402	3-1/4	14	1,245	.241	.367	949	.183	10,133		
B1400	13/16	14	155	.831	68	.367	35	.183	-	B1402	1-5/8	14	419	.483	318	.367	159	.183	3,840
72" BEAM OR COLUMN																			
A1200	1-5/8	12	589	.514	459	.400	299	.200	5,436	A1202	3-1/4	12	1,620	.286	.400	1,132	.200	12,500	
B1200	13/16	12	175	.946	74	.400	37	.200	-	B1202	1-5/8	12	503	.574	351	.400	176	.200	4,230
C1200	1-3/8	12	430	.595	289	.400	144	.200	3,485	C1202	2-3/4	12	1,203	.339	.400	710	.200	10,980	
D1200	1	12	256	.792	108	.400	54	.200	1,084	D1202	2	12	714	.457	468	.400	312	.200	5,230
E1200	2-7/16	12	1,108	.351	.400	632	.200	8,509	E1202	4-7/8	12	3,253	.191	.400	.200	17,023			
H1200	3-1/4	12	1,839	.269	.400	1,313	.200	10,782	H1202	6-1/2	12	5,361	.143	.400	.200	21,560			
A1400	1-5/8	14	405	.506	320	.400	160	.200	3,809	A1402	3-1/4	14	1,141	.286	.400	798	.200	9,340	
B1400	13/16	14	141	.989	57	.400	29	.200	-	B1402	1-5/8	14	384	.574	267	.400	134	.200	3,220
84" BEAM OR COLUMN																			
A1200	1-5/8	12	505	.700	337	.467	168	.233	4,061	A1202	3-1/4	12	1,388	.390	.467	832	.233	9,992	
B1200	13/16	12			54	.467	27	.233	-	B1202	1-5/8	12	431	.780	258	.467	129	.233	3100
C1200	1-3/8	12	369	.811	212	.467	106	.233	2,565	C1202	2-3/4	12	1,031	.461	.467	522	.233	8,670	
D1200	1	12	220	1.079	92	.467	58	.233	796	D1202	2	12	612	.623	344	.467	229	.233	3,842
E1200	2-7/16	12	950	.479	.467	464	.233	6,991	E1202	4-7/8	12	2,788	.260	.467	.233	13,993			
H1200	3-1/4	12	1,513	.366	.467	965	.233	8,988	H1202	6-1/2	12	4,595	.195	.467	.233	17,975			
A1400	1-5/8	14	348	.691	235	.467	118	.233	2,827	A1402	3-1/4	14	979	.390	.467	586	.233	7,682	
B1400	13/16	14			42	.467	21	.233	-	B1402	1-5/8	14	329	.781	197	.467	98	.233	2,370

When no numbers are shown, use the maximum uniform load.
Deflections are given in inches; loads in lb

Design Data – Metal Framing Channel**TABLE 3 (cont'd.)**

SINGLE CHANNEL								DOUBLE CHANNEL (Single Channels welded back-to-back)									
Cat. No.	Depth	Ga.	Maximum	1/180	1/360	Col.	Load	Maximum	1/180	1/360	Col.	Load	Load Defl.	Span			
			Uniform Load	Defl.	Load Defl.			Span	Span	Span				Defl.	Load		
96" BEAM OR COLUMN																	
A1200	1-5/8	12	441	.914	258	.533	129	.267	3,108	A1202	3-1/4	12	1,215	.509	.533		
B1200	13/16	12			42	.533	21	.267	-	B1202	1-5/8	12	378	1,019	197	.533	
C1200	1-3/8	12	323	1.059	163	.533	81	.267	1,960	C1202	2-3/4	12	903	.603	.533		
D1200	1	12	192	1.40	998	.533	49	.267	-	D1202	2	12	535	.813	263	.533	
E1200	2-7/16	12	831	.730		.533	355	.267	5,423	E1202	4-7/8	12	2,440	.340	.533		
H1200	3-1/4	12	1,323	.478		.533	739	.267	7,059	H1202	6-1/2	12	4,021	.255	.533		
A1400	1-5/8	14	304	.903	180	.533	90	.267	2,615	A1402	3-1/4	14	856	.509	.533		
B1400	13/16	14			32	.533	16	.267	-	B1402	1-5/8	14	288	1,020	150	.533	
108" BEAM OR COLUMN																	
A1200	1-5/8	12	393	1.156	204	.600	102	.300	2,456	A1202	3-1/4	12	1,080	.644	.600		
B1200	13/16	12			33	.600	16	.300	-	B1202	1-5/8	12	355	1,290	156	.600	
C1200	1-3/8	12	288	1.350	128	.600	64	.300	-	C1202	2-3/4	12	801	.763	632	.600	
D1200	1	12	171	1.783	76	.600	38	.300	-	D1202	2	12	476	1,029	208	.600	
E1200	2-7/16	12	739	.790	561	.600	281	.300	4,291	E1202	4-7/8	12	2,169	.430	.600		
H1200	3-1/4	12	1,176	.605		.600	584	.300	5,579	H1202	6-1/2	12	3,574	.323	.600		
A1400	1-5/8	14	270	1.141	142	.600	71	.300	1,708	A1402	3-1/4	14	761	.644	.600		
B1400	13/16	14			25	.600	13	.300	-	B1402	1-5/8	14	255	1,290	119	.600	
120" BEAM OR COLUMN																	
A1200	1-5/8	12	354	1.425	165	.667	83	.333	-	A1202	3-1/4	12	971	.795	.667		
B1200	13/16	12			27	.667	13	.333	-	B1202	1-5/8	12	301	1.588	126	.667	
C1200	1-3/8	12	259	1.663	104	.667	52	.333	-	C1202	2-3/4	12	721	.941	512	.667	
D1200	1	12	154	2.202	62	.667	31	.333	-	D1202	2	12	428	1.271	168	.667	
E1200	2-7/16	12	665	.976	455	.667	227	.333	3,478	E1202	4-7/8	12	1,951	.531	.667		
H1200	3-1/4	12	1,059	.746		.667	473	.333	4,521	H1202	6-1/2	12	3,216	.398	.667		
A1400	1-5/8	14	244	1.413	114	.667	57	.333	-	A1402	3-1/4	14	685	.796	.667		
B1400	13/16	14			21	.667	10	.33	-	B1402	1-5/8	14	230	1.600	96	.667	
144" BEAM OR COLUMN																	
A1200	1-5/8	12			115	.800	57	.400	-	A1202	3-1/4	12	810	1.145	566	.800	
-										B1202	1-5/8	12		88	.800	44	.400
C1200	1-3/8	12			72	.800	36	.400	-	C1202	2-3/4	12	601	1.350	355	.800	
E1200	2-7/16	12	554	1.400	315	.800	158	.400	-	E1202	4-7/8	12	1,626	.764	.800	852	.400
H1200	3-1/4	12	883	1.075	657	.800	328	.400	-	H1202	6-1/2	12	2,680	.573	.800	1,873	.400
A1400	1-5/8	14			80	.800	40	.400	-	A1402	3-1/4	14	571	1.146	399	.800	
-										B1402	1-5/8	14		67	.800	33	.400

When no numbers are shown, use the maximum uniform load.
Deflections are given in inches; loads in lb

Engineering Data & Specifications

Design Data – Metal Framing Channel




TABLE 3 (cont'd.)

SINGLE CHANNEL							DOUBLE CHANNEL (Single Channels welded back-to-back)						
Cat. No.	Depth	Ga.	Maximum	1/180	1/360	Col. Load	Maximum	1/180	1/360	Col. Load			
			Uniform Load	Defl.	Load Defl.		Span	Span					
168" BEAM OR COLUMN													
A1200	1-5/8	12		84	.933	-	42	.467		-	A1202	3-1/4	12
-											B1202	1-5/8	12
C1200	1-3/8	12		53	.933	-	27	.467		-	C1202	2-3/4	12
E1200	2-7/16	12	475	1.912	233	-	.933	116	.467	-	E1202	4-7/8	12
H1200	3-1/4	12	756	1.463	482	-	.933	241	.467	-	H1202	6-1/2	12
A1400	1-5/8	14		60	.933	-	30	.467		-	A1402	3-1/4	14
-											B1402	1-5/8	14
192" BEAM OR COLUMN													
-											A1202	3-1/4	12
-											-		
-											C1202	2-3/4	12
E1200	2-7/16	12		178	1.07	-	89	.533		-	E1202	4-7/8	12
H1200	3-1/4	12	661	1.91	369	-	1.07	185	.533	-	H1202	6-1/2	12
-											A1402	3-1/4	14
-											-		
216" BEAM OR COLUMN													
-											A1202	3-1/4	12
-											-		
-											C1202	2-3/4	12
E1200	2-7/16	12		140	1.20	-	70	.600		-	E1202	4-7/8	12
H1200	3-1/4	12		292	1.20	-	146	.600		-	H1202	6-1/2	12
-											A1402	3-1/4	14
-											-		
240" BEAM OR COLUMN													
-											A1202	3-1/4	12
-											-		
-											C1202	2-3/4	12
E1200	2-7/16	12		114	.334	-	57	.667		-	E1202	4-7/8	12
H1200	3-1/4	12		236	.334	-	118	.667		-	H1202	6-1/2	12
-											A1402	3-1/4	14
-											-		

When no numbers are shown, use the maximum uniform load.
Deflections are given in inches; loads in lb

Design Data – Metal Framing Channel**TABLE 4****Safe bearing loads for 1-5/8" channel and combinations.**





Safety factor of 2-1/2




Section	Recommended Load in lb	Section	Recommended Load in lb	Section	Recommended Load in lb
A1200	5000	A1200	3500	A1200	8000
A1400	3500	A1400	2500	A1400	5500
B1200	6000	B1200	4000	B1200	9000
B1400	3400	B1400	2600	B1400	4800
C1200	5000	C1200	3500	C1200	8000
E1200	5000	E1200	3500	E1200	8000
H1200	4000	H1200	2000	H1200	5500

TABLE 5**Design load table for typical channel connections.**



Safety factor of 2-1/2 based on ultimate strength of the connection. Load diagrams indicate up to three design loads, for 12 gauge and 14 gauge channel applications.

90° Fittings (When used in position shown)





AB202	A1200 A1400	1500 lb 1000 lb	AB203	A1200 A1400	2000 lb 1500 lb	AB201	700 lb
AB202	A1200 A1400	1000 lb 650 lb	AB213 AB214	A1200 A1400	3000 lb 2000 lb	AB20	1500 lb

AB202	A1200 A1400	1000 lb 650 lb	AB213 AB214	A1200 A1400	3000 lb 2000 lb	AB20	1500 lb	
AB205 AB216	A1200 A1400	2000 lb 2000 lb	AB204 AB215	A1200 A1400	1500 lb 1000 lb	AB206	A1200 A1400	1000 lb 800 lb

Flat Plate Fittings





AB205 AB216	A1200 A1400	2000 lb 2000 lb	AB204 AB215	A1200 A1400	1500 lb 1000 lb	AB206	A1200 A1400	1000 lb 800 lb
----------------	----------------	--------------------	----------------	----------------	--------------------	-------	----------------	-------------------

Engineering Data & Specifications

SECTION 8

Design Applications

CANTILEVER BEAMS




$$V_{\max.} = P$$

$$M_{\max.} = Pl$$




$$\Delta_{\max.} = \frac{Pl^3}{3EI}$$



$$V_{\max.} = W$$

$$M_{\max.} = \frac{Wl^2}{2}$$

$$\Delta_{\max.} = \frac{Wl^3}{8EI}$$




$$V_{\max.} = P$$

$$M_{\max.} = Pb$$

$$\Delta_{\max.} = \frac{Pb^2(3l-b)}{6EI}$$



SIMPLE BEAMS




$$R = \frac{P}{2}$$

$$V_{\max.} = \frac{P}{2}$$

$$M_{\max.} = \frac{Pl}{4}$$

$$\Delta_{\max.} = \frac{Pl^3}{48EI}$$




$$R = \frac{W}{2}$$

$$V_{\max.} = \frac{W}{2}$$

$$M_{\max.} = \frac{Wl}{8}$$

$$\Delta_{\max.} = \frac{5Wl^3}{384EI}$$




$$R_1 = \frac{Pb}{l}$$

$$R_2 = \frac{Pa}{l}$$

$$V_{\max.} = \frac{Pa}{l}$$


$$M_{\max.} = \frac{Pab}{l}$$



$$\Delta_{\max. \text{ at } x} = \sqrt{\frac{a(a+2b)}{3}}$$

$$\Delta_{\max.} = \frac{Pab(a+2b)\sqrt{3a(a+2b)}}{27EI/l}$$

BEAMS FIXED ON ONE END, SUPPORTED AT OTHER





$$R_1 = \frac{5P}{16}$$

$$V_{\max.} = \frac{11P}{16}$$

$$M_{\max.} = \frac{3Pl}{16}$$

$$\Delta_{\max. \text{ at } x=0.447l} = \frac{Pl^3}{EI}$$



$$R_1 = \frac{Pb^2}{2l^3}(a+2l)$$


$$R_2 = \frac{Pa}{2l^3}(3l^2-a^2)$$



$$M_{\text{at point of load}} = R_1 a$$

$$M_{\text{at fixed end}} = \frac{Pab}{2l^2}(a+l)$$


BEAMS FIXED AT BOTH ENDS



$$V_{\max.} = \frac{P}{2}$$

$$M_{\max.} = \frac{Pl}{8}$$


$$\Delta_{\max.} = \frac{Pl^3}{192EI}$$



$$V_{\max.} = \frac{W}{2}$$

$$M_{\max.} = \frac{Wl}{12}$$

$$\Delta_{\max.} = \frac{Wl^3}{384EI}$$



$$R_1 = \frac{Pb^2}{l^3}(3a+b)$$

$$R_2 = \frac{Pa^2}{l^3}(a+3b)$$



$$M_1 = \frac{Pab^2}{l^2}$$

$$M_2 = \frac{Pa^2b}{l^2}$$

$$\Delta_{\text{Deflection}} =$$

$$E - \text{Modulus of Elasticity}$$

$$I - \text{Moment of Inertia}$$

R - Reaction

M - Moment

P - Concentrated load


V - Total uniform load

W - Shear

Design Applications**TABLE 6****Conversion Factors for Beams with Various Static Loading Conditions**

Load tables on pages 104 through 108 for A, B, C, E, and H series channel are for single span beams supported at the ends. These can be used in the majority of cases. There are times when it is necessary to know what happens with other loading

and support conditions. Some common arrangements are shown in Table 6. Simply multiply the loads from the Design Load Tables times the factors given in Table 6. Examples shown on page 112.

LOAD AND SUPPORT CONDITION	LOAD FACTOR	DEFLECTION FACTOR
1. Simple Beam - Uniform Load 	1.00	1.00
2. Simple Beam - Concentrated Load at Center 	.50	1.25
3. Simple Beam - Two Equal Concentrated Loads at 1/4 Points 	1.00	1.10
4. Beam Fixed at Both Ends - Uniform Load 	1.50	.30
5. Beam Fixed at Both Ends - Concentrated Load at Center 	1.00	.40
6. Cantilever Beam - Uniform Load 	.25	2.40
7. Cantilever Beam - Concentrated Load at End 	.12	3.20
8. Continuous Beam - Two Equal Spans - Uniform Load on One Span 	1.30	.92
9. Continuous Beam - Two Equal Spans - Uniform Load on Both Ends 	1.00	.42
10. Continuous Beam - Two Equal Spans - Concentrated Load at Center of One Span 	.62	.71
11. Continuous Beam - Two Equal Spans - Concentrated Load at Center of Both Spans 	.67	.48

Engineering Data & Specifications

Design Applications

EXAMPLE I

PROBLEM:

Determine the load and deflection of an A1200 beam continuous over one support and loaded uniformly on one span.



SOLUTION:

- From load table 3 for A1200 the load for a 5'0" span is 706 lb and deflection is .358".
- Multiply by factors from Table 6.
Load = 706 lb x 1.30 = 917.8 lb
Deflection = .358 x .92 = .329"


COLUMN LOADING

The load bearing capacity of column or compression members is a function of the inherent configurational strength, the unbraced length and design of the end connections.

Values of axial column loading given in Table 3 were calculated using a rotationally free and translation fixed correction at each end (see illustration I). This gives an end condition constant (K) of 1.

ILLUSTRATION I

COLUMN HEIGHT



K value

.65

.80

1.0

1.2

END CONDITION CODE



Rotation fixed and translation fixed



Rotation free and translation fixed



Rotation fixed and translation free

TABLE 7

Load Carrying Capacities of Hot Rolled Steel Rod

Nominal Rod Dia.	Root Area Thread	Design Load lb for Serv. Temperature	
		343°C (650°F)	399°C (750°F)
3/8	.068	610	540
1/2	.126	1130	1010
5/8	.202	1810	1610
3/4	.302	2710	2420
7/8	.419	3770	3360

Dimensions are in inches.
Safety factor of 5.

TABLE 8

Rod Size Determined by Pipe Size for Fire Protection

Pipe Size	Rod Size
3/4 to 2	3/8
2-1/2 to 3-1/2	1/2
4 to 5	5/8
6	3/4
8 to 12	7/8

Dimensions are in inches.

SECTION 8**Engineering Data & Specifications****Design Applications****TABLE 9****Maximum Spacing between Pipe Supports**

Steel Pipe																			
Nom. Pipe Size (inches)	1/2	3/4	1	1-1/2	2	2-1/2	3	3-1/2	4	5	6	8	10	12	14	16	18	20	24
Max. Spacing (feet)	5	6	7	9	10	11	12	13	14	16	17	19	22	23	25	27	28	30	32
Copper Pipe																			
Nom. Pipe Size (inches)	1/2	3/4	1	1-1/4	1-1/2	2	2-1/2	3	3-1/2	4									
Max. Spacing (feet)	5	6	6	7	8	9	10	10	11	12									

TABLE 10**Minimum Spacing (inches) between Centers of Standard Pipe When Using Superstrut #702 Pipe Straps**

Nom. Pipe Size (inches)	1/2	3/4	1	1-1/4	1-1/2	2	2-1/2	3	3-1/2	4	5	6	8
1/2	1-3/16												
3/4	1-5/16	1-7/16											
1	1-1/2	1-5/8	1-3/4										
1-1/4	1-3/4	1-7/8	2	2-1/4									
1-1/2	1-15/16	2-1/16	2-3/16	2-7/16	2-9/16								
2	2-3/16	2-5/16	2-1/2	2-3/4	2-7/8	3-1/8							
2-1/2	2-7/16	2-9/16	2-3/4	3	3-1/8	3-3/8	3-5/8						
3	2-13/16	2-15/16	3-1/16	3-5/16	3-7/16	3-3/4	4	4-5/16					
3-1/2	3-1/8	3-1/4	3-3/8	3-5/8	3-3/4	4-1/16	4-5/16	4-5/8	4-15/16				
4	3-7/16	3-9/16	3-15/16	4-1/16	4-3/8	4-5/8	4-15/16	5-1/4	5-9/16				
6	4-3/4	4-7/8	5	5-1/4	5-3/8	5-5/8	5-7/8	6-3/16	6-1/2	6-13/16	7-7/16	8-1/8	
8	5-7/16	6	6-1/8	6-3/8	6-1/2	6-3/4	7	7-5/16	7-5/8	8	8-9/16	9-1/4	10-3/8

Design Applications**TABLE 11****Standard Dimensions and Weights of Piping Materials and Conduit**

Mechanical (ANSI & API Standard, Schedule 40)					
Nominal Std. Pipe Size (inches)	Pipe O.D. (inches)	Coupling O.D. (inches)	Weights of Pipe lb/ft	Weight of Pipe Filled w/Water lb/ft	
1/2	.84	1.06	.85		.98
3/4	1.05	1.31	1.13		1.36
1	1.32	1.58	1.68		2.05
1 - 1/4	1.66	1.90	2.27		2.92
1 - 1/2	1.90	2.20	2.72		3.60
2	2.38	2.75	3.65		5.11
2 - 1/2	2.88	3.25	5.79		7.87
3	3.50	4.00	7.58		10.78
3 - 1/2	4.00	4.63	9.11		13.39
4	4.50	5.00	10.79		16.30
5	5.56	6.30	14.62		23.28
6	6.63	7.39	18.97		31.48
8	8.63	9.23	28.56		50.24
10	10.75		41.00		74.00
12	12.75		50.00		99.00
14	14.00		64.00		122.00
16	16.00		63.00		142.00
18	18.00		71.00		172.00
20	20.00		79.00		205.00
22	22.00		87.00		240.00
24	24.00		95.00		277.00
26	26.00		103.00		322.00
28	28.00		111.00		364.00
30	30.00		119.00		410.00

Electrical Conduit					
Nominal Conduit Size	Rigid Steel			Thin Wall (EMT)	
	Conduit O.D. (inches)	Weight of Conduit lb/ft	Weight of Conduit w/Non-lead Covered Conductor lb/ft	Conduit O.D. (inches)	Weight of Conduit lb/ft
1/2	.84	.85	1.04	.71	.29
3/4	1.05	1.13	1.40	.92	.44
1	1.32	1.68	2.35	1.16	.64
1 - 1/4	1.66	2.28	3.58	1.51	.95
2	2.38	3.68	7.21	2.20	1.40
2 - 1/2	2.88	5.82	10.22	2.88	2.30
3	3.50	7.62	14.51	3.50	2.70
4	4.50	10.89	21.48	4.50	4.00

Includes weight of heaviest conductor combination.

SECTION 8
Engineering Data & Specifications
Design Applications
TABLE 12
Extra Strong Pipe (ANSI & API Standard, Schedule 80)

A.S.A. B36.10 SCHEDULE NOS. AND NOMINAL WALL THICKNESS DESIGNATIONS	Nominal Pipe Size (inches)	O.D. (inches)	Wall Thickness (inches)	I.D. (inches)	Weight of Pipe lb/ft	Water Weight per ft of Pipe lb	Weight of Pipe Filled w/Water lbs/ft
	3/8	.675	.126	.423	.74	.061	.801
	1/2	.840	.147	.546	1.09	.101	1.191
	3/4	1.050	.154	.742	1.47	.188	1.668
	1	1.315	.179	.957	2.17	.311	2.481
	1-1/4	1.660	.191	1.278	3.00	.555	3.555
EXTRA STRONG PIPE and SCHEDULE 80 PIPE (through 8")	1-1/2	1.900	.200	1.500	3.63	.765	4.395
	2	2.375	.218	1.939	5.03	1.279	6.309
	2-1/2	2.875	.276	2.323	7.66	1.834	9.497
	3	3.500	.300	2.900	10.30	2.860	13.160
	3-1/2	4.000	.318	3.364	12.55	3.850	16.350
	4	4.500	.337	3.826	15.00	4.980	19.980
EXTRA STRONG PIPE (10" through 24" OD)	5	5.563	.375	4.813	20.80	7.890	28.690
	6	6.625	.432	5.761	28.60	11.290	39.890
	8	8.625	.500	7.625	43.40	19.790	63.200
	10	10.750	.500	9.750	54.70	32.300	87.000
	12	12.750	.500	11.750	65.40	47.000	112.400
	14 OD	14.000	.500	13.000	72.10	57.500	129.600
	16 OD	16.000	.500	15.000	82.80	76.500	159.300
	18 OD	18.000	.500	17.000	93.50	98.400	191.900
	20 OD	20.000	.500	19.000	104.10	122.800	226.900
	24 OD	24.000	.500	23.000	125.50	180.100	305.600
SCHEDULE 80 PIPE (10" through 24" OD)	10	10.750	.593	9.564	64.300	31.100	95.400
	12	12.750	.687	11.376	88.50	44.000	132.500
	14 OD	14.000	.750	12.500	106.10	53.200	159.300
	16 OD	16.000	.842	14.314	136.50	69.700	206.200
	18 OD	18.000	.937	16.126	170.80	88.500	259.300
	20 OD	20.000	1.031	17.938	208.90	109.400	318.300
	24 OD	24.000	1.218	21.564	296.40	158.300	454.700

TABLE 13
Pipe Covering Weights (Thickness intended as guide, only)

Thickness and weight of calcium silicate covering.

Nominal Pipe Size	260° Thick. (inches)	260° lb/ft	360° Thick. (inches)	360° lb/ft	440° Thick. (inches)	440° lb/ft	525° Thick. (inches)	525° lb/ft	600° Thick. (inches)	600° lb/ft	700° Thick. (inches)	700° lb/ft	800° Thick. (inches)	800° lb/ft
1	1	.68	1	.68	1	.68	1-1/2	1.19	1-1/2	1.19	1-1/2	1.19	1-1/2	1.19
1-1/4	1	.75	1	.75	1	.75	1-1/2	1.27	1-1/2	1.27	2	1.82		
1-1/2	1	.88	1	.88	1	.88	1-1/2	1.45	1-1/2	1.45	2	1.87		
2	1	1.01	1	1.01	1	1.01	1-1/2	1.53	1-1/2	1.53	2	2.50	2	2.50
2-1/2	1	1.15	1	1.15	1	1.15	1-1/2	1.69	1-1/2	1.69	2	2.50	2-1/2	3.22
3	1	1.28	1	1.28	1	1.28	1-1/2	2.09	1-1/2	2.09	2	2.98	2-1/2	3.98
3-1/2	1	1.44	1	1.44	1-1/2	2.29	1-1/2	2.29	2	3.00	2	3.12	2-1/2	4.30
4	1	1.60	1	1.60	1-1/2	2.49	1-1/2	2.49	2	3.49	2	3.49	2-1/2	4.62
5	1	1.84	1	1.84	1-1/2	2.84	1-1/2	2.84	2	3.97	2	3.97	2-1/2	5.92
6	1-1/2	3.13	1-1/2	3.13	1-1/2	3.13	1-1/2	3.13	2	4.54	2	4.54	2-1/2	6.75
8	1-1/2	4.06	1-1/2	4.06	1-1/2	4.06	1-1/2	4.06	2	5.56	2	5.56	2-1/2	7.61


Engineering Data & Specifications

SECTION 8

Design Applications

TABLE 14

Column Loading For Rack Construction

**GENERAL STORAGE RACKS****PALLET RACKS****BARREL RACKS****BULK FURNITURE RACKS****CABLE RACKS****BAR STOCK RACKS****DISPLAY RACKS****SPECIAL PURPOSE RACKS**

**For Uniform Loads on Horizontal Members
See Table 3**

ALLOWABLE LOAD IN LB PER UPRIGHT


Column Height	Cat. No.	NUMBER OF SHELVES PER UPRIGHT							
		2	3	4	5	6	7	8	9
6'	A1200	2237	1925	1650	1437	1290			
	A1202	4170	3580	3100	2730	2450			
	B1400	800	820	790	700	630			
	B1402	1930	1700	1500	1300	1190			
7'	A1200	2150	1850	1630	1425	1280	1150		
	A1202	4000	3525	3000	2700	2430	2200		
	B1400	650	790	760	685	615	550		
	B1402	1800	1650	1450	1300	1180	750		
8'	A1200	2000	1820	1600	1400	1250	1150	1050	
	A1202	3900	3475	3000	2700	2400	2185	2000	
	B1400	580	750	730	660	610	540	510	
	B1402	1650	1610	1450	1300	1160	940	970	
9'	A1200	1950	1780	1575	1400	1250	1130	1030	950
	A1202	3800	3400	3020	2675	2400	2180	1975	1800
	B1400		600	665	600	580	540	500	475
	B1402	1500	1500	1430	1275	1160	1000	900	800
10'	A1200	1870	1700	1500	1300	1200	1100	1000	900
	A1202	3600	3300	3000	2650	2350	2000	1975	1800
	B1400		550	650	625	580	535	490	450
	B1402	1450	1480	1400	1250	1140	1040	960	885
									825

SECTION 8

Engineering Data & Specifications


Design Applications – Mechanical Support

Example 1




Suspended column, carrying brackets, braced to the ceiling.

Example 2




Suspended column, holding bracket and console braced to wall.

Example 3



Trapeze with channels as cross members using beam clamps and hanger rods.


Example 5



Trapeze, constructed from channels, fittings.


The use of spot inserts is shown (SI400-1/2).

Example 4




Sketch depicts the use of beam clamps on slanted beams.






Example 6



Trapeze with S202 cross members using hanger rods and concrete inserts.

Engineering Data & Specifications**Design Applications – Mechanical Support****Example 7**

* NOTE: BRACE SHOULD BE USED FOR LENGTHS GREATER THAN 30"

Single-sided bracket application**Example 8****Single-sided bracket application****Example 9****Two-sided heavy duty application****Example 10****Heavy duty bracket application****Example 11****Brackets parallel to beam****Example 12****Brackets perpendicular to beam**

ALPHANUMERIC INDEX

Catalogue #	Page #	Catalogue #	Page #	Catalogue #	Page #	Catalogue #	Page #
50236	703-1-1/4EG42	AB100-1/414	AR1600HS9
50736	703-1EG42	AB100-3/414	AR1600KO9
50836	703-2EG42	AB100-3/814	AR1600P9
50936	703-3/4EG42	AB100-5/1614	AR1600S9
51036	811-1STR59	AB100-5/814	AR1600SW9
51136	811-2STR59	AB102-1/214	AW20425
452TB11	812-1EG59	AB102-1/414	AW205L25
460-10TB11	812-EG14	AB102-3/414	AW205R25
500SC36	813EG14	AB102-3/814	AW21425
503SC36	A100-1/2EGC13	AB102-5/814	AW215L25
512U32	A100-1/2EGC14	AB102-7/814	AW215R25
540-1/238	A100-1/4EGC13	AB20121	AW21925
540-3/438	A100-1/4EGC14	AB20221	AW22025
540-3/838	A100-3/413	AB20321	AW22425
540-5/838	A100-3/414	AB20421	AW22625
542-1/238	A100-3/8EGC13	AB20521	AW22825
542-3/838	A100-3/8EGC14	AB20620	B100-1/2EGC13
6H036	A100-5/16EGC13	AB20720	B100-1/2EGC14
6H046	A100-5/16EGC14	AB21321	B100-1/4EGC13
6H0-B46	A100-5/8EGC14	AB21421	B100-1/4EGC14
6H0-T36	A100-7/814	AB21621	B100-3/8EGC13
6H0-T46	A12009	AB21920	B100-3/8EGC14
6H0-TB46	A1200HS9	AB22020	B100-5/16EGC13
6H136	A1200KO9	AB22523	B100-5/16EGC14
6H146	A1200P9	AB22623	B12009
6H1-B46	A1200S9	AB22723	B1200HS9
6H1-T36	A1200SW9	AB22823	B1200P9
6H1-T46	A14009	AB23123	B1200S9
6H1-TB46	A1400HS9	AB23223	B1200SW9
6H236	A1400KO9	AB239-123	B14009
6H246	A1400P9	AB239-223	B20923
6H2 1/236	A1400S9	AB239-323	B21024
6H2-1/246	A1400SW9	AB24020	B302-1011
6H2-1/2-B46	A177-1/4X100EG14	AB241-1/220	B302-2011
6H2-B46	A177-1/4X125EG14	AB241-1/420	B802EG58
6H3-B46	A179-3/8X100EG14	AB241-3/420	B804EG10
6H3-SC36	A179-3/8X125EG14	AB241-3/820	B804NEOPWH10
6H3-SC46	A182-1/4X100EGC14	AB241-5/1620	B82258
6H3-TB46	A182-1/4X125EGC14	AB241-5/820	BR16009
6H436	A184-3/8X100EGC14	AB24220	BR1600HS9
6H446	A184-3/8X125EGC14	AB24524	BR1600P9
6H4-B46	A185-1/2X100EGC14	AB252-121	BR1600S9
6H4-TB46	A185-1/2X125EG14	AB252-221	BR1600SW9
6H536	A20810	AB252-321	C12009
6H546	A20824	AB252-421	C1200HS9
6H5-B46	A20923	AB25320	C20923
6H5-TB46	A21024	AB254L21	C21024
6H636	A21124	AB254R21	C302-1011
6H646	A21224	AB25520	C704A55
6H6-B46	A21310	AB25720	C708U49
6H736	A21324	AB260L21	C71051
6H746	A21358	AB260R21	C71150
6H7-B46	A21725	AB26120	C72053
6H836	A21825	AB26320	C72552
6H846	A243110	AB26520	C72653
6H8-B46	A302-1011	AB27421	C72750
6H936	A302-2011	AB27521	C72829
6H946	A570HDG34	AB284L22	C72955
6H9-B46	A59733	AB284R22	C73655
701-045PG42	A71645	AB288-1/224	C739H55
701-055PG42	A716-145	AB288-3/824	C739M55
701-065PG42	A716-1/245	AB288-5/824	C749N-1 1/854
701-075PG42	A716-1/445	AB29922	C749N-5/854
701-088PG42	A716-1-1/245	AB80359	C749N-7/854
701-100PG42	A716-1-1/445	AB81559	C75555
701-113PG42	A716-1-1/845	AB844PC10	C755-1A48
701-126PG42	A716-1-3/445	AB844PC59	C755-1B48
701-140PG42	A716-1-3/845	AB844PCGY10	C755-1C48
701-153PG42	A716-1-5/845	AB844PCGY59	C755-248
701-167PG42	A716-1-7/845	AB844PGC10	C755-2A48
701-180PG42	A716-245	AB844PGC59	C755-2B48
701-193PG42	A716-2-1/845	AB86659	C755-2C48
701-204PG42	A716-2-3/845	AB86759	C755-348
701-225PG42	A716-2-5/845	AB86859	C755-3A48
701-237PG42	A716-3/445	AB88048	C755-3B48
701-245PG42	A716-3/845	AB88148	C755-3C48
701-257PG42	A716-3-1/845	AB88559	C755-448
701-287PG42	A716-4-1/845	AC100-1/2EGC14	C755-4A48
701-294PG42	A716-5/845	AC100-1/4EG14	C755-4B48
701-306PG42	A716-7/845	AC100-3/4EGC14	C755-4C48
701-319PG42	A802EG58	AC100-3/8EGC14	C755-548
701-350PG42	A804EG10	AC100-5/8EG14	C755-5A48
701-356PG42	A804NEOPWH10	AN21124	C755-5B48
701-379PG42	A805EG58	AN27029	C755-5C48
701-400PG42	A809-3/4EG58	AN270-129	C755-648
701-450PG42	A82258	AN270-229	C755-6A48
701-556PG42	A85358	AP23228	C755-6B48
701-665PG42	A853L58	AP232SQ28	C755-6C48
701-876PG42	A85458	AP23528	C755-748
703-1/2EG42	A854L58	AP235SQ28	C755-7A48
703-1-1/2EG42	AB100-1/2EG14	AR16009	C755-7B48

ALPHANUMERIC INDEX

Catalogue #	Page #	Catalogue #	Page #	Catalogue #	Page #	Catalogue #	Page #
C755-7C	.48	E1200HS	.9	G2000	.60	RC-1-1/4	.37
C755-8	.48	E1200KO	.9	G2001	.60	RC-2-1/2	.37
C755-8A	.48	E1200P	.9	G2002	.60	RC-2-SC	.37
C755-8B	.48	E1200S	.9	G2003	.60	RC-3	.37
C755-8C	.48	E142-1/2X100EG	.15	G2004	.60	RC-3/4	.37
C755-8D	.48	E142-1/2X150EG	.15	G972HB1/2	.61	RC-3-1/2	.37
C755-8E	.48	E142-1/2X200EG	.15	H100-1/2EGC	.13	RC-4-SC	.37
C755-8F	.48	E142-1/2X225EG	.15	H100-1/2EGC	.14	RC729A	.55
C769	.55	E142-1/2X250EG	.15	H100-3/8EGC	.13	RCS-1	.37
C775L-1/2EG	.35	E142-1/2X275EG	.15	H100-3/8EGC	.14	RCS-1/2	.37
C775L-3/4EG	.35	E142-1/4X100EG	.15	H104-1/2X10EGC	.15	RCS-1-1/2	.37
C775L-3/8EG	.35	E142-1/4X150EG	.15	H104-1/4X10EGC	.15	RCS-1-1/4	.37
C775L-5/8EG	.35	E142-3/8X100EG	.15	H104-1X10EG	.15	RCS-2	.37
C775L-7/8EG	.35	E142-3/8X150EG	.15	H104-3/4X10EGC	.15	RCS-3/4	.37
C780	.55	E145-1/2EGC	.14	H104-3/8X10EGC	.15	RCS-3/8	.37
C781-1	.17	E145-1/4EGC	.14	H104-5/8X10EGC	.15	S202-15	.26
C781-1	.38	E145-1EGC	.14	H104-7/8X10EGC	.15	S202-21	.26
C781-1/2	.17	E145-3/4EGC	.14	H115	.17	S202-27	.26
C781-1/2	.38	E145-3/8EGC	.14	H119	.15	S202-33	.26
C781-3/4	.17	E145-5/8EG	.14	H1200	.9	S202-6	.26
C781-3/4	.38	E145-7/8EG	.14	H1200HS	.9	S202-9	.26
C781-3/8	.17	E146-1/4HDGC	.14	H1200KO	.9	S203-14	.26
C781-3/8	.38	E146-3/8HDGC	.14	H1200P	.9	S203-20	.26
C781-5/8	.17	E146-5/16HDGC	.14	H1200S	.9	S203-26	.26
C781-5/8	.38	E146-5/8HDGC	.14	H802	.58	S203-32	.26
C781-7/8	.17	E147-1/2EG	.15	H804	.10	S203-38	.26
C781-7/8	.38	E147-1/4EG	.15	H804NEOPWH	.10	S203-8	.26
C785A	.55	E147-3/4EG	.15	H805EG	.58	S204	.27
C786	.55	E147-3/8EG	.15	LKCPC050	.43	S205	.27
C789	.55	E147-5/16EG	.15	LKCPC075	.43	S217	.27
C790	.55	E147-5/8EG	.15	LKCPC100	.43	S218	.27
C804EG	.10	E147-7/8EG	.15	LKCPC125	.43	S222	.27
CB118	.44	E148-1/2EG	.15	LKCPC150	.43	S226	.27
CB118-047PG	.44	E148-1/4EG	.15	LKCPC200	.43	S247	.26
CB118-055PG	.44	E148-3/8EG	.15	LKCPC250	.43	S248	.26
CB118-070PG	.44	E148-5/8EG	.15	LKCPC300	.43	S249-14	.26
CB118-090PG	.44	E150S-1/2X1-1/2EG	.15	LKCPC350	.43	S249-20	.26
CB118-110PG	.44	E150S-1/2X2-1/2EG	.15	LKCPC400	.43	S249-26	.26
CB118-140PG	.44	E150S-1/2X2EG	.15	M718	.52	S249-32	.26
CB118-175PG	.44	E150S-1/2X3EG	.15	M732	.55	S249-38	.26
CB118-200PG	.44	E150S-3/8X1-1/2EG	.15	M732H	.55	S249-8	.26
CB118-250PG	.44	E150S-3/8X2-1/2EG	.15	M742R-1/2	.38	S250-12	.26
CB118-300PG	.44	E150S-3/8X2EG	.15	M742R-3/8	.38	S250-14	.26
CH118-047EG	.44	E150S-3/8X3EG	.15	M750	.55	S250-18	.26
CH118-055EG	.44	E151-1/2X10EG	.15	M775L-1/2EG	.35	S250-20	.26
CH118-081EG	.44	E151-1/2X4EG	.15	M775L-3/4EG	.35	S250-24	.26
CH118-110EG	.44	E151-1/2X6EG	.15	M775L-3/8EG	.35	S250-26	.26
CH118-125EG	.44	E151-1/2X8EG	.15	M775L-5/8EG	.35	S250-6	.26
CH118-135EG	.44	E151-3/8X10EG	.15	M777	.55	S250-8	.26
CH118-175EG	.44	E151-3/8X12EG	.15	M778	.55	S251-12	.26
CH118-205EG	.44	E151-3/8X4EG	.15	N205	.22	S251-14	.26
CH118-250EG	.44	E151-3/8X6EG	.15	N219	.22	S251-18	.26
CH118-300EG	.44	E151-3/8X8EG	.15	P716	.45	S251-20	.26
CH118-325EG	.44	E210	.24	P716-1	.45	S251-24	.26
CH118-375EG	.44	E802EG	.58	P716-1/2	.45	S251-26	.26
CH118-425EG	.44	E804EG	.10	P716-1/4	.45	S251-30	.26
CH118-475EG	.44	E809-3/4EG	.58	P716-1-1/2	.45	S251-32	.26
CL710	.51	EB118	.44	P716-1-1/4	.45	S251-36	.26
CM100-1/2	.13	EB118-047PG	.44	P716-2	.45	S251-38	.26
CM100-1/2	.14	EB118-055PG	.44	P716-2-1/2	.45	S256-12	.26
CM100-1/2B	.13	EB118-070PG	.44	P716-3	.45	S256-14	.26
CM100-1/4	.13	EB118-090PG	.44	P716-3/4	.45	S256-18	.26
CM100-1/4	.14	EB118-110PG	.44	P716-3/8	.45	S256-20	.26
CM100-3/8	.13	EB118-140PG	.44	P716-3-1/2	.45	S256-24	.26
CM100-3/8	.14	EB118-175PG	.44	P716-4	.45	S256-26	.26
CM100B-1/2	.14	EB118-200PG	.44	PC-1	.37	S256-6	.26
CN749N	.54	EB118-250PG	.44	PC-1/2	.37	S256-8	.26
CPC050	.43	EB118-300PG	.44	PC-1-1/2	.37	S541-3/8	.38
CPC075	.43	EC-1	.37	PC-1-1/4	.37	S716	.49
CPC100	.43	EC-1/2	.37	PC-2	.37	S730D	.55
CPC125	.43	EC-1/2	.37	PC2-1/2	.37	S730S	.55
CPC150	.43	EC-1-1/4	.37	PC-3	.37	SI400-1/2	.11
CPC200	.43	EC-2	.37	PC-3/4	.37	SI400-3/8	.11
CPC250	.43	EC-2-1/2	.37	PC-3/8	.37	TBQC050	.43
CPC300	.43	EC-3	.37	PC-3-1/2	.37	TBQC075	.43
CPC350	.43	EC-3/4	.37	PC-4	.37	TBQC100	.43
CPC400	.43	EF147-1/4EGC	.15	RA-160-10	.66	TBQC100	.43
CZ209	.23	EF147-3/8EGC	.15	RA160-12	.66	TBQC125	.43
D1200	.9	ES142-1/2X1-1/2	.54	RA225-10	.66	TBQC150	.43
D1200HS	.9	ES145-1/2	.14	RA225-12	.66	TBQC250	.43
D1200P	.9	ES145-3/8	.14	RA300-10	.66	TBQC300	.43
D1200S	.9	EZ209	.23	RA300-12	.66	TBQC350	.43
D1200SW	.9	G1017	.61	RA-BN-3/4	.66	TBQC400	.43
D209	.23	G1038	.60	RA-BN-5/8	.66	TC5363X	.46
D210	.24	G1038A	.60	RA-C	.66	TR292	.29
DB118	.44	G1038B	.60	RA-GP	.66	TR294	.29
DB118-047PG	.44	G1038C	.60	RA-RC	.66	TS272HDG	.29
DB118-055PG	.44	G1038CA	.60	RA-SC	.66	TS273HDG	.29
DB118-070PG	.44	G1038CX	.60	RC-1	.37	U501	.32
DB118-090PG	.44	G1038D	.60	RC-1/2	.37	U502	.32
E1200	.9	G1038E	.60	RC-1-1/2	.37	U504	.32

ALPHANUMERIC INDEX

Catalogue #	Page #	Catalogue #	Page #
U50532	WS716-647
U51032	WS716-6-1/247
U51432	WS716-747
U514-A32	X20122
U51532	X20422
U515-B32	X20720
U52033	X20820
U52133	X28922
U52233	X29922
U54333		
U54433		
U560-1/235		
U560-1/435		
U560-3/835		
U560-5/835		
U56234		
U56334		
U564-1/235		
U564-3/835		
U564-5/835		
U568-1EG35		
U568-2EG35		
U568-3EG35		
U568-4EG35		
U568-5EG35		
U568-6EG35		
U568-7EG35		
U568-8EG35		
U56934		
U570-133		
U570-233		
U576-1/239		
U576-3/839		
U577-1/239		
U579-1/239		
U579-3/839		
U71645		
U716-145		
U716-1/245		
U716-1/445		
U716-1-1/245		
U716-1-1/445		
U716-1-1/845		
U716-1-3/845		
U716-1-5/845		
U716-2-1/845		
U716-2-3/845		
U716-3/445		
U716-3/845		
U716-5/845		
U716-7/845		
U71745		
U86147		
UC100-1/213		
UC100-1/214		
UC100-1/413		
UC100-1/414		
UC100-3/813		
UC100-3/814		
UM56234		
US56234		
US56334		
W716-1-1/2PG47		
W716-1-1/4PG47		
W716-1-3/4PG47		
W716-1PG47		
W716-2-1/2PG47		
W716-2-1/4PG47		
W716-2-3/4PG47		
W716-2PG47		
W716-3/4PG47		
W716-3PG47		
W716-4PG47		
WS716-147		
WS716-1-1/247		
WS716-1-1/447		
WS716-1-3/447		
WS716-247		
WS716-2-1/247		
WS716-2-1/447		
WS716-2-3/447		
WS716-347		
WS716-3/447		
WS716-3-1/247		
WS716-3-1/447		
WS716-3-3/447		
WS716-447		
WS716-4-1/247		
WS716-547		
WS716-5-1/247		

Superstrut[®]

NOTES

Thomas&Betts
