

## DC Motor & Motion Sensor

### Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

### Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4" and 6"** polymeric collar with lightweight built-in back draft damper
- IC Rated up to R40 insulation

### Motor

- Power rating of 120V/60Hz
- Permanently lubricated motor
- Energy efficient, brushless **two speed DC motor** for low speed continuous ventilation from 30-80 CFM
- Quick installation of motor and impeller assembly
- Built-in dip switch to adjust high fan speed setting from 80 to 140 CFM
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit
- Life Hours: 60,000

### Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

### Motion Sensor

- Activates higher motor speed and delayed timer
- Adjustable timer from 5 to 60 minutes


### Warranty

- 2 year limited warranty



*Refer to Pg. J16  
for Fan Curve (1)*

### Grille



Cat. No.		ODU814M				
Static pressure	Inches w.g.	0.1"				
Duct diameter	Inches	4" & 6"				
Air volume	CFM	80	90	110	120	140
Noise	Sone	0.3	0.3	0.6	0.8	1.1
Power consumption	Watts	9	9	10	10	11
Energy efficiency	CFM/Watts	8.9	10	11	12	14
Power rating	V/Hz.	120/60				

## DC Motor & Humidity Sensor

### Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

### Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Includes **detachable 4" and 6"** round duct with built-in draft damper
- IC Rated up to R40 insulation

### Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, quick installation motor
- Energy efficient, brushless **two speed DC motor** for low speed continuous ventilation from 30-80 CFM
- Built-in dip switch to adjust high fan speed setting from 80 to 140 CFM
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit
- Life Hours: 60,000

### Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

### Humidity Sensor

- Adjustable from 50 to 100% relative humidity
- Adjustable timer from 5 to 60 minutes

### Warranty

- 2 year limited warranty

### Lighting

#### FANLIGHTS

Included:  
1 - 23 Watt GU24  
Compact Fluorescent  
Lamp & 1 - 4 Watt  
Incandescent Lamp



#### LED FANLIGHTS

Included:  
10 Watt LED Lamp



ODU814H



ODU814LH & ODU814LLH

**Refer to Pg. J16  
for Fan Curve (1)**

Model	FANS				FANLIGHTS		LED FANLIGHTS		
Cat. No.	ODU814H				ODU814LH		ODU814LLH		
Static pressure	Inches w.g.	0.1"							
Duct diameter	Inches	4"				6"			
Air volume	CFM	80	90	110	120	90	110	120	140
Noise	Sone	0.7	0.7	0.6	1.2	0.3	0.5	0.8	1.1
Power consumption	Watts	5.5	7.0	11.9	13.0	5.5	10.0	11.5	14.5
Energy efficiency	CFM/Watts	14.55	12.86	9.24	9.23	16.36	11.00	10.43	9.66
Power rating	V/Hz.	120/60							
Weight	lbs	10.6							
Master Qty.		1							



## Humidity Sensor

### Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

### Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4" and 6"** round duct with built-in draft damper
- IC Rated up to R40 insulation

### Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor
- Low RPM for quiet operation
- Built-in overload disconnect for safety and longer motor life
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

### Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

### Humidity Sensor

- Adjustable from 50 to 100% relative humidity
- Adjustable timer from 5 to 60 minutes

### Warranty

- 2 year limited warranty

### Lighting

#### FANLIGHTS

Included:  
1 - 23 Watt GU24  
Compact Fluorescent  
Lamp & 1 - 4 Watt  
Incandescent Lamp



#### LED FANLIGHTS

Included:  
10 Watt LED Lamp



OD80H & OD110H



OD80LH & OD110LH  
OD80LLH & OD110LLH

**Refer to Pg. J16  
for Fan Curve (2)**



Model		FANS		FANLIGHTS		LED FANLIGHTS	
Cat. No.		OD80H	OD110H	OD80LH	OD110LH	OD80LLH	OD110LLH
Static pressure	Inches w.g.	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"
Air volume	CFM	80	110	80	110	80	110
Noise	Sone	<b>0.7</b>	<b>0.9</b>	<b>0.7</b>	<b>0.6</b>	<b>0.7</b>	<b>0.6</b>
Power consumption	Watts	33.3	35.8	28	35	28	35
Energy efficiency	CFM/Watts	2.40	3.08	2.86	3.14	2.86	3.14
Power rating	V/Hz.	120/60	120/60	120/60	120/60	120/60	120/60
Duct diameter	Inches	4" & 6"	4" & 6"	4" & 6"	4" & 6"	4" & 6"	4" & 6"
Weight	lbs	9.9	9.9	9.9	9.9	9.9	9.9
Master Qty.		1	1	1	1	1	1

## Recessed Fan Lights

### Housing Dimensions

- 12-5/8" L x 8" W x 7-5/8" H

### Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **4" and 5"** metal duct adapter with built-in back draft damper
- Adjustable lamp base holder for flushed lighting mounts
- IC rated up to R40 insulation

### Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor
- Quick installation of motor and impeller assembly
- Quiet operation and minimal vibration transfer
- Built-in overload disconnect for safety and longer motor life
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

### Grille & Trim

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

### Warranty

- 2 year limited warranty

### Lighting

#### FANLIGHTS

Not Included:  
1 - 16 Watt GU24  
Base Compact  
Fluorescent Lamp



#### LED FANLIGHTS

Included:  
4.5 Watt LED Lamp,  
MR16 trim



OE80RL



OE80RLL

**Refer to Pg. J16  
for Fan Curve (3)**

Model		FANLIGHTS	LED FANLIGHTS
Cat. No.		OE80RL	OE80RLL
Static pressure	Inches w.g.	0.1"	0.1"
Air volume	CFM	80	80
Noise	Sone	1.0	1.0
Power consumption	Watts	18.8	18.8
Energy efficiency	CFM/Watts	4.25	4.25
Power rating	V/Hz.	120/60	120/60
Duct diameter	Inches	4" & 5"	4" & 5"
Weight	lbs	9.7	9.7
Master Qty.		1	1



## Housing Dimensions

- 9-1/8" L x 9-1/8" W x 7-5/8" H

## Housing

- Heavy-duty steel housing coated with rust proof paint
- Adjustable double bar hanger system that extends up to 24"
- 4" exhaust pipe connection
- Wired for both fan or fanlight
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable, and sturdy

## Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor with ball bearings designed for continuous use
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

## Grille

- Contemporary design - with or without light kit
- Durable white ABS for easy cleaning
- Torsion spring clips included for easy installation
- Electronic ballast

## Warranty

- 2 year limited warranty

## Lighting

### FANLIGHTS

Included:  
2 - 18 Watt Flicker-Free,  
Electronic Ballast  
Compact Fluorescent Lamps



FANLIGHTS MODEL

*Refer to Pg. J16 for Fan Curve (4) or  
Refer to Pg. J17 for Fan Curve (5)*



**TITLE 24**  
COMPLIANT



Model		FANS				FANLIGHTS			
Cat. No.		OD80*	OD90*	OD110*	OD120*	OD80L	OD90L	OD110L	OD120L
Static pressure	Inches w.g.	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"
Air volume	CFM	80	90	110	120	80	90	110	120
Noise	Sone	0.8	1.0	1.5	2.0	0.5	0.7	1.2	1.5
Power consumption	Watts	27.9	28.4	30.6	32.1	31.6	32.1	33.7	37.0
Energy efficiency	CFM/Watts	2.87	3.17	3.59	3.74	2.53	2.80	3.26	3.24
Speed	RPM	946	965	1,083	1,153	990	1,017	1,126	1,201
Current	Amps	.18	.18	.19	.2	.27	.26	.27	.30
Power rating	V/Hz.	120/60	120/60	120/60	120/60	120/60	120/60	120/60	120/60
Duct diameter	Inches	4"	4"	4"	4"	4"	4"	4"	4"
Motor type		Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed
Weight	lbs	10	10	10	10	10	10	10	10
Master Qty.		4	4	4	4	4	4	4	4

## Deluxe Heat Fan Light

### Housing Dimensions

- 10-1/2" L x 11-3/8" W x 7-5/8" H

### Housing

- Corrosion-Resistant Galvanized Steel
- Double hanger bar mounting brackets that are adjustable up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Effortless side electrical connection
- Includes detachable 4" polymeric collar with lightweight built-in back draft damper

### Motor

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when used with a GFCI branch circuit

### Heater

- 1000W PTC ceramic heater with metal blower
- Thermal auto-self protection
- Electric shock protection

### Grille

- Thermal paint 22 gauge sheet metal
- Torsion spring clips included for easy installation

### Warranty

- 2 year limited warranty on parts

### Lighting


#### FANLIGHTS

Not Included:  
2 - 23 Watt GU24  
Compact Fluorescent  
Lamps



*Refer to Pg. J17  
for Fan Curve (6)*

### Grille



Cat. No.		ODHFL110
Static pressure	Inches w.g.	0.1"
Duct diameter	Inches	4" & 6"*
Air volume	CFM	110
Noise	Sone	0.3
Power consumption	Watts	9
Energy efficiency	CFM/Watts	8.9
Power rating	V/Hz.	120/60

\*6" polymeric collar available upon request

[www.orbitelectric.com](http://www.orbitelectric.com)



## Economy Plus Series

### Housing Dimensions

- 9-1/8" L x 9-1/8" W x 7-5/8" H

### Housing

- Heavy-duty steel housing coated with rust proof paint
- Adjustable double bar hanger system that extends up to 24"
- Includes 4" exhaust pipe connection
- Wired for both fan only or fanlight
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable and sturdy

### Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor designed to continuously active
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

### Grille

- Contemporary design - with or without light kit
- Durable white ABS for easy cleaning
- Torsion spring clips included for easy mounting
- Electronic ballast

### Warranty

- 2 year limited warranty

### Lighting

#### FANLIGHTS

Included:  
2 - 18 Watt Flicker-Free,  
Electronic Ballast Compact  
Fluorescent Lamps



**FANLIGHTS MODEL**  
**Refer to Pg. J17**  
**for Fan Curve (7) & (8)**

Model		FANS			FANLIGHTS		
Cat. No.		OEP80*	OEP90*	OEP110	OEP80L	OEP90L	OEP110L
Static pressure	Inches w.g.	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"
Air volume	CFM	80	90	110	80	90	110
Noise	Sone	1.3	1.5	2.0	1.0	1.1	1.0
Power consumption	Watts	31.2	24.5	27	29.2	24.5	27.3
Energy efficiency	CFM/Watts	2.56	3.67	4.07	2.79	3.67	4.03
Speed	RPM	1,189	1,227	1,393	1,198	1,251	1,458
Current	Amps	.16	.21	.16	.24	.21	.22
Power rating	V/Hz.	120/60	120/60	120/60	120/60	120/60	120/60
Duct diameter	Inches	4"	4"	4"	4"	4"	4"
Motor type		Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed
Weight	lbs	9.2	9.9	9.9	9.2	9.9	9.9
Master Qty.		4	4	4	4	4	4



**TITLE 24**  
COMPLIANT





### Housing Dimensions

- **OE50:** 7-3/4" L x 7-3/4" W x 4-1/4" H
- **OE70 & OE80:** 8-1/4" L x 8" W x 4-1/4" H

### Housing

- Heavy-duty Galvanized Steel
- Mounting tabs for easy installation
- 4" exhaust pipe connection, except for OE50 is 3"
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable and sturdy



### Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor designed to be continuously active
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

### Grille

- Contemporary design
- Durable white ABS
- Gloss finish for "quick wipe" cleaning
- Torsion spring clips included for easy mounting

### Warranty

- 2 year limited warranty



Cat. No.		OE50	OE70	OE80
Static pressure	Inches w.g.	0.1"	0.1"	0.1"
Air volume	CFM	50	70	80
Noise	Sone	3.0	3.5	4.0
Power consumption	Watts	36.5	27.1	30.8
Energy efficiency	CFM/Watts	1.37	2.58	2.60
Speed	RPM	1,839	1,223	1,334
Current	Amps	.51	.24	.27
Power rating	V/Hz.	120/60	120/60	120/60
Duct diameter	Inches	3"	4"	4"
Motor type		Shaded Pole	Enclosed	Enclosed
Weight	lbs	4.6	6.2	6.2
Master Qty.		12	12	12





## Housing Dimensions

- **OSP50 & OSP70:** 7-1/2" L x 7-1/4" W x 3-5/8" H
- **OSP70L:** 7-1/2" L x 7-1/4" W x 5-5/8" H

## Housing

- Corrosion-Resistant Galvanized Steel
- Built-in mounting ears for ceiling or wall installation
- Torsion mounting
- Wired for both fan or fanlight
- Includes **detachable 3" or 4"** polymeric collar

## Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated motor with plug for continuous run and easy removal
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet performance
- Removable Centrifugal-type Blower Wheel
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

## Grille

- Modern and elegant design
- Durable Polymeric Resin

## Warranty

- 2 year limited warranty

## Lighting

### FANLIGHTS

Included:  
1 - 13 Watt GU24  
Compact Fluorescent  
Lamp



OSP50 & OSP70



OSP70L



Model		FANS		FANLIGHTS
Cat. No.		OSP50	OSP70	OSP70L
Air volume	CFM	50	70	70
Noise	Sone	3.5	3.5	3.5
Power consumption	Watts	44.3	62.8	62.8
Energy efficiency	CFM/Watts	0.53	1.14	1.14
Power rating	V/Hz.	120/60	120/60	120/60
Duct diameter	Inches	3"	4"	4"
Finish color		White	White	White
Weight	lbs	3.6	3.6	4.6
Master Qty.		12	12	12



### Housing Dimensions

- 7-5/8" L x 6-3/4" W x 4-1/8" H

### Housing

- Galvanized housing resists humid conditions & changing attic temperatures, unlike plain steel housing used in many vents
- Ceiling/wall thickness indicator markings & built-in mounting tabs for quick installation
- Built-in junction box for easy wiring
- Precision balanced, molded fan blade for quiet operation
- Molded duct adaptor with built-in damper



### Motor and Heating

- Easy removal and installation of motor assembly with keyhole mounting bracket
- Permanently lubricated motor with plug designed for continuous use
- Units and service parts are CSA listed

### Grille

- Attractive molded grille with spring clips for smooth fit against ceiling or wall
- Dishwasher-safe grille with Polycarbonate Light Lens for easy homeowner cleaning

Grille




← 8 1/2" square →

### Warranty

- 2 year limited warranty

Housing & Motor



Cat. No.		OS50	OS70
Air volume	CFM	50	70
Noise	Sone	3.2	4.0
Power rating	V/Hz.	120/60	120/60
Duct diameter	Inches	4"	4"
Finish color		White	White
Master Qty.		12	12



## Housing Dimensions

- 7-5/8" L x 6-3/4" W x 4-1/8" H

## Housing

- Galvanized housing resists humid conditions & changing attic temperatures, unlike plain steel housing used in many vents
- Ceiling/wall thickness indicator markings & built-in mounting tabs for quick installation
- Built-in junction box for easy wiring
- Precision balanced, molded fan blade for quiet operation
- Molded Duct Adaptor with built-in damper
- Combination Lamp Compartment & Aluminum Reflector
- Built-in medium base lampholder included



## Motor and Heating

- 950 W fan-forced heating element
- Easy removal and installation of motor assembly with keyhole mounting bracket
- Permanently lubricated motor with plug for quick activations
- Units and service parts are CSA listed

## Grille

- Attractive molded grille with spring clips for smooth fit against ceiling or wall
- Dishwasher-safe grille with Polycarbonate Light Lens for easy homeowner cleaning




## Warranty

- 2 year limited warranty

## Housing & Motor

5 3/4"




Cat. No.		OEHL70
Air volume	CFM	70
Noise	Sone	4.0
Duct diameter	Inches	4"
Finish Color		White
Master Qty.		4



Orbit's highly certified and energy efficient ventilation fan and fanlights are available in contractor packs for large projects and quick installations.


- *Easy and secure installation for reduced labor and costs*
- *Universal housing for reduced inventory and greater flexibility*
- *Fitted with the best fan motors in the ventilation market lasting up to 30,000 hours*
- *Optimal energy efficiency-reduces utility costs by up to 50%*
- *No sharp edges to reduce injury in the field*

## Ordering Guide



### STEP 1

Select Housing




### STEP 2

Select  
Grille + Motor



### ACCESSORIES 1

Fanlight  
Conversion Kits



### ACCESSORIES 2

Grille  
Replacement



## CONTRACTOR PACKS

### STEP 1

Select Housing

### STEP 2



Select  
Grille + Motor









### ACCESSORIES 1

Fanlight  
Conversion Kits

### ACCESSORIES 2

Grille  
Replacement

Cat.No.		Description	Compatible Models
OE50H		Economy Housing 7-3/4"L x 7-3/4"W x 4-1/4"H 6 Per Carton	OE50
OSPH		Standard Housing 7-1/2"L x 7-1/4"W x 3-5/8"H 6 Per Carton	OSP50
OEPH		Economy Plus Housing 9-1/8"L x 9-1/8"W x 7-5/8"H 4 Per Carton	OEP80 OEP80L OEP90 OEP90L OEP110 OEP110L
ODH		Deluxe Housing 9-1/8"L x 9-1/8"W x 7-5/8"H 4 Per Carton	OD80 OD80L OD90 OD90L OD110 OD110L

Cat.No.		Air Volume (CFM)	Description	Compatible Models
OE50F	 + 	50CFM	Economy 6 Per Carton 1 Grille + 1 Fan Motor	OE50
OSP50F	 + 	50CFM	Standard 6 Per Carton 1 Grille + 1 Fan Motor	OSP50
OEP80F OEP90F OEP110F	 + 	80CFM 90CFM 110CFM	Economy Plus 4 Per Carton 1 Grille + 1 Fan Motor	OEP80 OEP90 OEP110
OD80F OD90F OD110F	 + 	80CFM 90CFM 110CFM	Deluxe 4 Per Carton 1 Grille + 1 Fan Motor	OD80 OD90 OD110

Cat.No.	Grille + light	Description	Compatible Models
OVFM	 + 	4 Per Carton 2 - 18W Lamps + Fanlight Grille + Ballast	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L

Cat.No.		Description	Compatible Models
OEP-G		Economy Plus Grille	OEP80 OEP90 OEP110
OD-G		Deluxe Grille	OD80 OD90 OD110 OD120
OEP-G		Deluxe & Economy Plus Grille for Fanlights	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L
OEP-L		Deluxe & Economy Plus Lens	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L



## HUMIDITY SENSORS

- Manual On/Off Control
- LED indicator light
- May be used to comply with: ASHRAE, Energy Star, LEED & CALGreen
- 1 year limited warranty
- Stylish decorator design with wall plate included

Cat. No.	Description	Color (Cat. No. - Color Code)		Std. Pkg.
		White	Almond	
FS-100	Fan Switch Electrical Input: 120 volts @ 60Hz Max. Fan Load: 1/8th hp or 3 amps	FS-100-W	FS-100-A	3
FS-200	Fan & Light Switch Electrical Input: 120 volts @ 60Hz Max. Fan Load: 1/8th hp or 3 amps Max. Light Load: 400 watt for a fluorescent light or 500 watt for an incandescent light	FS-200-W	FS-200-A	3

NEW

TITLE 24  
COMPLIANT

FS-100



blue LED light  
Condensation Sentry  
fan ON  
fan OFF



FS-200

blue LED light  
Condensation Sentry  
light ON/OFF  
fan ON/OFF

## DEHUMIDISTAT SENSORS

- RH Range: 20% - 80%
- Differential: 8%RH Max
- Mounting: Wall Mount
- Color: White
- Switch: SPST
- Voltage: 125/250 VAC
- FLA: 7.5Amps @125 VAC, 3.3Amps @ 250 VAC
- Cycle Rating: 50,000 automatic @ 140°F (60°C), 6,000 manual cycles
- Operating temperature: 32°F to 140°F (0°C to 60°C)
- RoHS Compliance
- Approvals: CSA LR 32079

Cat. No.	Description	Std. Pkg.
DS-2080	Wall Mounted Dehumidistat Sensor	25



DS-2080

NEW

TITLE 24  
COMPLIANTRESIDENTIAL GRADE  
DECORATIVE SWITCHES

## Features:

- 120~277 VAC
- Rocker-type
- Impact-Resistant Thermoplastic Body
- With Combination Head Screws

Cat. No.	Description	Color (Cat. No. - Color Code)				Std. Pkg.	Master Carton
		White	Ivory	Black	Almond		
2DS15	Double Rocker Switch, 15A, 120~277V Single-Pole Side Wire only	2DS15-W	2DS15-I	2DS15-BK	2DS15-A	10	200
3DS15	Triple Rocker Switch, 15A, 120~277V Single-Pole Push-In Back Wire only, with Ground Pigtail	3DS15-W	3DS15-I	3DS15-BK	3DS15-A	10	200



2DS15



3DS15



## FAN ACCESSORIES

### 45LT-D

#### Compatible Models

OD80 OEP80  
OD90 OEP90  
OD110 OEP110  
OD120  
OD80L OEP80L  
OD90L OEP90L  
OD110L OEP110L  
OD120L

**NEW**

Cat. No.	Description	Std. Pkg.
T46	Transition 4" X 6"	1
45LT-D	Ceiling Radiation Fire Damper	1
GUEBA	GU24 to Edison Base adapter	10



T46



45LT-D



GUEBA



## REPLACEMENT BULBS

Cat. No.	Description	Std. Pkg.
PL13-GU-27K	13W GU24 Base Compact Fluorescent, 2700K	1
PL23-GU-41K	23W GU24 Base Compact Fluorescent, 4100K	1
R30-GU-41K	Compact Fluorescent Lamp PAR30, GU24 Base, 16W, 4100K	1



PL13-GU-27K



PL23-GU-41K



R30-GU-41K

## REPLACEMENT GRILLES

### OFLGML

#### Compatible Models

ODU814H  
OD80H  
OD110H

### ORLTML

#### Compatible Models

OE80RL

**NEW**


Cat. No.	Description	Std. Pkg.
OFLGML	Fan Light Grille Module with 10W LED Lamp	1
ORLTML	Recess Fan Light Trim Module with 6W MR16 LED Lamp	1




OFLGML




ORLTML




See Pg.1 or Pg.2 for Fan Info



See Pg.3 for Fan Info




See Pg.4 for Fan Info




See Pg.5 for Fan Info







See Pg.5 for Fan Info



See Pg.6 for Fan Info



See Pg.7 for Fan Info



See Pg.7 for Fan Info