



**Hard at Work Since 1948**

| Clamp Meters     |   | Pg 3                |       |
|------------------|---|---------------------|-------|
| AMP-210 .....    | 5 | ACD-10 PLUS .....   | 8     |
| AMP-220 .....    | 5 | ACD-14 PLUS .....   | 8     |
| AMP-310 .....    | 5 | ACD-14-PRO .....    | 9     |
| AMP-320 .....    | 5 | ACDC-3400 IND ..... | 9     |
| AMP-330 .....    | 5 | RS-1007 .....       | 10    |
| ACD-50NAV .....  | 6 | AC50A .....         | 10    |
| ACD-51NAV .....  | 6 | LH41A .....         | 10    |
| ACDC-52NAV ..... | 6 | ACD-6 PRO .....     | 10    |
| ACDC-54NAV ..... | 6 | ELS2A .....         | 10/56 |
| AMP-25 .....     | 7 |                     |       |
| ACD-20SW .....   | 8 |                     |       |
| ACD-23SW .....   | 8 |                     |       |

| Digital Multimeters |    | Pg 11        |    |
|---------------------|----|--------------|----|
| AM-510 .....        | 13 | AM-500 ..... | 16 |
| AM-530 .....        | 13 | DM73C .....  | 16 |
| AM-570 .....        | 13 | PM51A .....  | 16 |
| 37XR-A .....        | 14 | PM55A .....  | 16 |
| 38XR-A .....        | 14 |              |    |
| HD110C .....        | 15 |              |    |
| HD160C .....        | 15 |              |    |

| Electrical Testers |    | Pg 17         |    |
|--------------------|----|---------------|----|
| INSP-3 .....       | 18 | VP-440 .....  | 21 |
| LT-10 .....        | 18 | ST-101B ..... | 21 |
| TIC 300 PRO .....  | 19 | ST-102B ..... | 21 |
| TIC 410A .....     | 19 | PK-110 .....  | 22 |
| PRM-6 .....        | 20 | PY-1A .....   | 22 |
| MO-100 .....       | 20 | LAN-1 .....   | 22 |
| VP-1000SB .....    | 21 |               |    |

| Wire Tracers • Locators |    | Pg 23          |    |
|-------------------------|----|----------------|----|
| AT-7020 .....           | 24 | AT-1000 .....  | 28 |
| AT-7030 .....           | 24 | CT-100 .....   | 29 |
| AT-3500 .....           | 26 | CT-326-C ..... | 29 |
| AT-4000-A SERIES .....  | 27 | BT-250 .....   | 29 |
| AT-2000-A SERIES .....  | 28 |                |    |

| Power Quality • Insulation • Ground Resistance |    | Pg 31           |    |
|--|----|-----------------|----|
| AMB-45 .....                                   | 32 | AMC-3 .....     | 34 |
| AMB-25 .....                                   | 32 | AMC-4 .....     | 34 |
| AMB-50 .....                                   | 33 | GP-2A .....     | 35 |
| AMB-55 .....                                   | 33 | DGC-1000A ..... | 35 |
| AMB-110 .....                                  | 33 |                 |    |
| AMB-3 .....                                    | 34 |                 |    |
| AMC-2 .....                                    | 34 |                 |    |

| Thermometers        |    | Pg 37         |    |
|---------------------|----|---------------|----|
| IR-700 SERIES ..... | 38 | TMD-56 .....  | 41 |
| IR-450 .....        | 39 | TR200-A ..... | 42 |
| IR608A .....        | 39 | TR300 .....   | 42 |
| THWD-3 .....        | 40 |               |    |
| TH-3 .....          | 40 |               |    |
| TH-1 .....          | 40 |               |    |
| THWD-5 .....        | 40 |               |    |

| Environmental   |    | Pg 43           |    |
|-----------------|----|-----------------|----|
| MT-10 .....     | 44 | CO2-100 .....   | 48 |
| TMA5 .....      | 44 | CO2-200 .....   | 48 |
| TMA10A .....    | 45 | TACH-10 .....   | 49 |
| TMA40-A .....   | 45 | TACH20 .....    | 49 |
| TMA-21HW .....  | 46 | LM-100 .....    | 49 |
| RLD-1 .....     | 46 | LM-120 .....    | 49 |
| GSD600 .....    | 47 | LM-200LED ..... | 49 |
| ULD-300 .....   | 47 | SM-10 .....     | 50 |
| TMULD-300 ..... | 47 | SM-20-A .....   | 50 |
| CM-100 .....    | 48 | SM-CAL1 .....   | 50 |

| Solar • Battery • Components |    | Pg 51                    |    |
|------------------------------|----|--------------------------|----|
| <b>Solar Testers</b>         |    | <b>Component Testers</b> |    |
| SOLAR-100 .....              | 52 | CR50A .....              | 54 |
| SOLAR-600 .....              | 52 | LCR55A .....             | 54 |
| <b>Battery Testers</b>       |    | <b>Relays</b>            |    |
| BAT-250 .....                | 53 | R-115S .....             | 54 |
| BAT-500 .....                | 53 | RC-120S .....            | 54 |

| Accessories          |    | Pg 55                |    |
|----------------------|----|----------------------|----|
| Test Leads .....     | 56 | Carrying Cases ..... | 57 |
| Hanging Strap .....  | 56 | Fuse Directory ..... | 58 |
| Line Splitter .....  | 56 | Software .....       | 58 |
| Current Clamps ..... | 56 | Product Index .....  | 59 |
| Thermocouple .....   | 56 |                      |    |

## No Hassle Warranty

No waiting. No shipping charges.

Amprobe is committed to delivering the highest quality test and measurement products and provides a 1 year warranty with most products. The length of the product warranty is stated in the user manual that comes with each product, which can be downloaded from [www.Amprobe.com](http://www.Amprobe.com).

To better serve you, in the unlikely event that an Amprobe product requires warranty service, Amprobe authorizes over-the-counter



product exchange from the authorized Amprobe distributor for which the product was purchased, within 30 days from the date of purchase for products with a list price up to \$500. For products with a list price greater than \$500 or for issues encountered after the first 30 days but within the warranty period, please contact the Amprobe Service Department at 1-877-AMPROBE for warranty services.

# Clamp Meters

## Test Voltage and Amperage Simultaneously

The ACD-14-PRO offers a complete range of measuring functions for both HVAC and electrical applications. This modern clamp meter features a large backlit LCD dual display and is capable of simultaneously displaying voltage and amps.

The ACD-14-PRO is packed with features including TRMS, low pass filter, inrush current, frequency, resistance, capacitance, temperature, DC micro-amps, Amp-Tip and non-contact voltage detection.



NEW  
2016



★★★★★  
**TOP RATED**

# AMP-200 and AMP-300 Series TRMS and Motor Maintenance Clamp Meters

The AMP-200 and -300 Series True-RMS Clamp Meters offer a complete range of measurement functions for modern electrical environments, motor testing and HVAC applications. All models feature True-RMS sensing, low pass filters and fast response processors for quick, error-free measurements. The new Amp-Tip function allows for precise measurement of current down to the tenth of an Amp, and a third input jack on the AMP-300 Series enables motor rotation and 3-phase sequence testing. These clamps are surprisingly versatile, designed to eliminate the need for multiple tools and provide all-in-one measurement capabilities.

- **True-RMS** for noisy environments
- **Motor testing capabilities** (AMP-300 Series)
- **HVAC features** (AMP-300 Series)
- **Capacitance measurement**
- **Amp-Tip function** for precise measurements on small wires
- **Low pass filter** for variable frequency drives
- **Peak hold** (AMP-330)
- **Work light** (AMP-330)
- **Safety rated:**
  - **CAT III 600 V** (AMP-200 Series, AMP-310, AMP-320)
  - **CAT III 1000 V, CAT IV 600 V** (AMP-330)



**AMP-330**  
Industrial Motor  
Maintenance  
Clamp Meter

**Clamp Meters**

| FEATURE                        | AMP-210                                       | AMP-220             | AMP-310      | AMP-320                        | AMP-330      | BEST ACCURACY |   |
|--------------------------------|---|---------------------|--------------|--------------------------------|--------------|---------------|---|
| <b>Electrical</b>              | <b>AC Current</b>                             | 0 to 600.0 A        |              |                                |              | 0 to 1000 A   | ±1.8% + 5LSD (50 to 100 Hz)<br><b>AMP-330:</b> ±1.8% + 5LSD (40 to 100 Hz)  |
|                                | <b>DC Current</b>                             | –                   | 0 to 600.0 A | –                              | 0 to 600.0 A | 0 to 1000 A   | ±2.0% + 5LSD<br><b>AMP-330:</b> ±1.8% + 5LSD  |
|                                | <b>AC Voltage</b>                             | 0 to 600.0 V        |              |                                |              | 0 to 1000.0 V | ±1.0% + 5LSD (50 to 60 Hz)<br><b>AMP-330:</b> ±0.8% + 5LSD (50 to 60 Hz)  |
|                                | <b>DC Voltage</b>                             | 0 to 600.0 V        |              |                                |              | 0 to 1000.0 V | ±1.0% + 5LSD<br><b>AMP-330:</b> ±0.8% + 5LSD  |
|                                | <b>Resistance</b>                             | 0.0 kΩ to 60.00 kΩ  |              |                                |              |               | ±1.0% + 5LSD  |
|                                | <b>Frequency</b>                              | 5.00 Hz to 999.9 Hz |              |                                |              |               | ±1.0% + 5LSD (600 V range)<br>±1.0% + 5LSD (600 A range)<br><b>AMP-330:</b> ±1.0% + 5LSD (1000 V range)<br>±1.0% + 5LSD (1000 A range)  |
|                                | <b>Amp-Tip Function</b> (precise low current) | •                   | •            | •                              | •            | •             |   |
| <b>Accommodates Conductors</b> | 1.18" (30mm)                                  | 1.37" (35mm)        | 1.18" (30mm) | 1.37" (35mm)                   | 2.0" (51mm)  |               |   |
| <b>HVAC</b>                    | <b>Capacitance</b>                            | 0.0 μF to 2500 μF   |              |                                |              |               | ±2.0% + 4LSD  |
|                                | <b>DCμA</b>                                   | –                   | –            | 0.0 to 2000 μA                 |              |               | ±1.0% + 5LSD  |
|                                | <b>Temperature</b>                            | –                   | –            | -40.0 to 752°F, -40.0 to 400°C |              |               | -40.0 to 14.0°F (±1.0% +3.0°F),<br>>14.0 to 99.9°F (±1.0% +1.5°F),<br>100 to 752°F (±1.0% +2°F),<br>-40.0 to -10.0°C (±1.0% +1.5°C),<br>>-10.0 to 99.9°C (±1.0% +0.8°C),<br>100 to 400°C (±1.0% +1°C) |
| <b>Motor</b>                   | <b>3-Phase and Motor Rotation Indication</b>  | –                   | –            | •                              | •            | •             |   |
|                                | <b>Inrush Current</b>                         | –                   | •            | •                              | •            | •             |   |
|                                | <b>Peak Hold (Crest)</b>                      | –                   | –            | –                              | –            | •             |   |
|                                | <b>Low Pass Filter</b>                        | •                   | •            | •                              | •            | •             |   |

### Recommended Accessories

**TL35B**

Test Leads (AMP-210 and AMP-220 only) (See Page 56)



**TL-300**

Test Leads (All AMP-200 and AMP-300 Series) (not shown)

**ELS2A**

AC Line Splitter (See Page 56)



★★★★★  
**TOP RATED**

**"This product makes my job easier"**

*"The Amprobe 600A AC TRMS makes my electrical life easier when I am performing electrical diagnostics on HVAC units. Its made to fit well in my hand with no slips. It is easy to adjust to different settings with just my thumb, allowing me to test various components without stopping to use two hands to change settings. Most of all I can trust amprobe to keep me safe."*

- AMP-320 customer review

**INCLUDED ACCESSORIES:** Test leads, user manual, batteries (installed)  
AMP-310, AMP-320, AMP-330 only: Alligator Clip Set, Banana plug  
K-type Thermocouple



AMP-330

## Navigator™ CAT IV Power Quality Clamp Meters

These power quality clamp meters measure power and power factor, total harmonic distortion, individual harmonics, as well as AC/DC voltage, current, capacitance, inrush current analysis, and phase sequence. The low pass filter enables voltage and current measurement on variable frequency drives. The Navigator™ joy stick allows quick selection of the numerous measurement features on the large LCD display. Built for rugged industrial environments with CAT IV 600 V/CAT III 1000 V safety rating.



Rated 5 Out of 5 Stars



ACDC-54NAV

Joystick control detail



- THD (total harmonic distortion) and individual harmonics 1-25
- Power (KW) and power factor (0-1) indicates electrical usage and system efficiency
- True-RMS provides accuracy and dependability
- Low pass filter for variable frequency drives
- Inrush current measurement for motors
- Phase rotation indication
- MAX/MIN and smart data hold
- Peak hold
- Auto flashlight when clamping
- Large backlit display with analog bar graph
- Overmold body absorbs shock – drop-proof to 4 ft (1.2 m)
- Safety Rated CAT IV 600 V

| FEATURE                             | ACD-50NAV                       | ACD-51NAV                          | ACDC-52NAV                      | ACDC-54NAV                         | BEST ACCURACY                                |
|-------------------------------------|---------------------------------|------------------------------------|---------------------------------|------------------------------------|--|
| AC Current                          | 100.00 A, 600.0 A               |                                    |                                 | 100.00 A, 1000.0 A                 | +/- (1.5% rdg + 5 LSD)                       |
| DC Current                          | -                               | -                                  | 100.00 A, 600.0 A               | 100.00 A, 1000.0 A                 | +/- (1.5% rdg + 5 LSD)                       |
| AC Voltage                          | 100.00 V, 1000 V                |                                    |                                 |                                    | +/- (1.0% rdg + 5 LSD)                       |
| DC Voltage                          | 100.00 V, 1000 V                |                                    |                                 |                                    | +/- (0.7% rdg + 2 LSD)                       |
| Resistance                          | 1.0000 kΩ, 10.000 kΩ, 100.00 kΩ |                                    |                                 |                                    | +/- (1.0% rdg + 3 LSD)                       |
| Frequency                           | 20.0 Hz to 10 kHz               |                                    |                                 |                                    | +/- (0.5% rdg + 3 LSD)                       |
| Capacitance                         | 4.000 μF, 4000 μF               |                                    |                                 |                                    | +/- (1.9% rdg + 8 LSD)                       |
| DCμA                                | -                               | 1000.0 μA                          | -                               | -                                  | +/- (1.7% rdg + 2 LSD)                       |
| Temperature                         | -                               | -50°F → 1832°F<br>(-50°C → 1000°C) | -                               | -50°F → 1832°F<br>(-50°C → 1000°C) | +/- (1% rdg + 1°C)                           |
| THD<br>(Total Harmonics Distortion) | 0.1% → 100.0%                   |                                    |                                 |                                    | +/- (3.0% rdg + 10 LSD)                      |
| Individual Harmonics                | 1 → 25                          |                                    |                                 |                                    | -  |
| Power                               | 10 kW → 600 kW                  |                                    | 10 kW → 1000 kW                 |                                    | ±(A, error×V, reading + V, error×A, reading) |
| Power Factor                        | -1.00 → 1.00                    |                                    |                                 |                                    | +/- 3 degrees                                |
| Accommodates Conductors             | Up to 1.45" (37 mm) in diameter |                                    | Up to 1.60" (40 mm) in diameter |                                    |  |

### Recommended Accessories

**TL35B**  
Test Leads  
(See Page 56)

**ELS2A**  
AC Line Splitter  
(See Page 56)



**INCLUDED ACCESSORIES:** Test leads, user manual, batteries (installed), thermocouple (ACD-51NAV and ACDC-54NAV only)



### TOP RATED ★★★★★

**"Awesome CAT IV clamp meter with Power Factor**

*Great design, easy to use even with voltage gloves. Nothing out there that even comes close. When I'm suited up in arc flash clothing & wearing 1000 volt gloves the ACDC-54NAV provides peace of mind. I feel very confident placing the clamp around a 480 volt energized feeder since the meter/leads/gloves are all 1000 volt rated.*

- ACDC-54NAV customer review



ACD-50NAV

ACD-51NAV

ACDC-52NAV

ACDC-54NAV

### Navigate Through Any Job

| Job Function                   | Applications  | Model  |
|--------------------------------|---|--|
| <b>Industrial Electricians</b> | <p><b>Motor Testing.</b> Use inrush current to test motors capacitance to check start up capacitors and phase rotation to measure three-phase systems</p> <p><b>Power Quality.</b> Quickly determine the efficiency of an electrical system by measuring power factor and working power measurements. Check for harmful harmonics while you perform daily system checks</p> <p><b>Transformers.</b> The Navigator™ Clamp is the ideal tool for maintenance and installation of transformers and advanced equipment</p>  | <p><b>ACDC-52NAV</b><br/><b>ACDC-54NAV</b></p> |
| <b>Facilities Maintenance</b>  | <p><b>System Monitoring.</b> Assess and monitor the condition of various systems and advanced equipment such as power quality analyzers</p> <p><b>Performance Testing.</b> Verify system efficiency and quickly troubleshoot issues to minimize costly downtime by performing load studies, motor testing system checks</p>   | <b>ACD-50NAV</b>                               |
| <b>HVAC Technicians</b>        | <p><b>System Monitoring.</b> Maintain large, complex HVAC systems in factories, data centers, hospitals and commercial buildings</p> <p><b>Performance Testing.</b> Best tool for technicians who need the following critical measurements during HVAC system checks and repairs:</p> <ul style="list-style-type: none"> <li>• Capacitance for checking startup capacitors</li> <li>• Micro Amps for the verification of the flame sensors</li> <li>• Temperature for checking cooling/heating performance</li> <li>• Inrush current for verification of the compressor motor</li> <li>• Low-pass filter to allow measurement of the variable frequency drives</li> </ul> | <b>ACD-51NAV</b>                               |

★★★★★  
**TOP RATED**

## AMP-25 AC/DC TRMS Mini-Clamp

Small size doesn't mean small features. The Amprobe AMP-25 Mini-Clamp is pocket-sized, enabling quick and easy spot checks of electrical systems. With its rugged construction and CAT III 600V rating, the AMP-25 is a must-have professional troubleshooting tool for commercial electricians and electrical contractors. The AMP-25 is designed to measure AC/DC load current and inrush current for motors. Essential features like True-RMS, non-contact voltage and low pass filter make this clamp stand tall next to clamps twice its size. With the AMP-25, you never have to sacrifice performance for size.

- True-RMS for noisy environments provides accuracy and dependability
- AC & DC current to 300 A (10mA resolution)
- Low pass filter for variable frequency drives
- Inrush current for motor start-up monitoring
- Non-contact voltage detection (NCV)
- Jaw opening to 1 in (25 mm)
- Autoranging
- DCA zero and data hold
- Auto power off
- Large LCD backlit display
- Safety Rated CAT III 600 V

| FEATURE             | AMP-25          | BEST ACCURACY   |
|---------------------|-----------------|---|
| AC Current          | 60.00 / 300.0 A | +/- (1.5% + 5 LSD) @ 50 to 100 Hz ≥ 3 A<br>+/- (2.5% + 5 LSD) @ 100 to 400 Hz ≥ 3 A |
| DC Current          | 60.00 / 300.0 A | +/- (1.5% + 5 LSD) @ 300 A range  |
| Low Pass Filter     | •               |   |
| True-RMS            | •               |   |
| Inrush Current      | •               |   |
| Non-Contact Voltage | •               |   |
| Data Hold           | •               |   |

**INCLUDED ACCESSORIES:** Carrying case, two 1.5 V LR44 batteries installed and user manual



**AMP-25**  
AC/DC TRMS  
Mini-Clamp

**Clamp Meters**

### Recommended Accessories

**ELS2A**  
AC Line  
Splitter  
(See Page 56)



**Troubleshoot electrical systems** and measure AC/DC load current on exposed wires in a breaker panel.



**Utilize the inrush current** function for motor start-up monitoring.



**The non-contact voltage (NCV)** function checks for voltage presence.



**Pocket-sized** for quick and easy spot checks of electrical systems.

★★★★★  
**TOP RATED**

**"Small size, good accuracy & resolution"**  
"I find the AMP-25 Mini-Clamp is a good all around tool for measuring current in tight MCC enclosures other hard to reach locations. It is small enough, and rugged enough, to keep in my toolbox for easy access but has the accuracy and resolution I need for motor or LP balance checks."

- AMP-25 customer review

## Swivel™ Clamp Meters ★★★★★ TOP RATED

Get fast and easy testing for HVAC and electrical applications. See measurements in tight or inconvenient spaces with the patented 180-degree rotating head design of Amprobe's Swivel™ Clamp Meters. The slim jaw puts all features within reach for one-handed operation.

- 180-degree rotating head
- VolTect™ non-contact voltage detection
- Audible continuity
- Auto ranging for quick checks
- Manual ranging for precise measurements
- Data hold



ACD-23SW

| FEATURE                                | ACD-20SW  | ACD-23SW                               | BEST ACCURACY  |
|--|---|--|--|
| True-RMS                               | -   | •                                      | -  |
| AC Current                             | 40.00 A, 400.0 A  |  | +/- (2.0% rdg + 10 LSD) 50 Hz → 60 Hz                            |
| AC Voltage                             | 4.000 V, 40.00 V, 400.0 V, 600.0 V                        |  | +/- (1.2% rdg + 8 LSD)<br>→ 50 Hz → 500 Hz at 4 V → 400 V ranges |
| DC Voltage                             | 400.0 mV, 4.000 V, 40.00 V, 400.0 V, 600.0 V              |  | +/- (0.5% rdg + 2 LSD)   |
| Resistance                             | 400.0 Ω, 4.000 kΩ, 40.00 kΩ, 400.0 kΩ, 4.000 MΩ, 40.00 MΩ |  | +/- (1.0% rdg + 4 LSD) at 400 Ω → 400 kΩ ranges                  |
| Capacitance                            | -   | 4.000 μF, 40.00 μF, 400.0 μF, 4.000 μF | +/- (3.0% rdg + 5 LSD) on 40 μF → 400 μF ranges                  |
| Temperature                            | -   | -30°F → 400°F, (-35°C → 400°C)         | +/- (1.0% + 2°F) 32°F → 400°F<br>+/- (1.0% + 1°C) 0°C → 400°C    |
| Diode Test                             | •   | -                                      | -  |
| VolTect™ non-contact voltage detection | 70 V → 600 VAC (50 Hz → 60 Hz)                            |  | -  |
| Backlight                              | -   | •                                      | -  |
| Accommodates Conductors                | Up to 1.18" (30 mm) in diameter                           |  |  |

**INCLUDED ACCESSORIES:** Test leads, battery (installed), user manual, carrying case, K-type thermocouple (ACD-23SW only)



## ACD-10 PLUS Clamp Multimeter with Uniquely Thin Jaws

With thinner jaws than standard clamp multimeters (only 0.4"/10 mm thick), the ACD-10 PLUS and ACD-14 PLUS allow access to tight measurement areas and still accommodate conductors up to 1"/25 mm.

### Recommended Accessories

**FOR: ACD-20SW, ACD-23SW, ACD-10 PLUS and ACD-14PLUS**

- TL35B** Test Leads (See Page 56)
- ELS2A** AC Line Splitter (See Page 56)



## ACD-14 PLUS Dual Display Digital Clamp Multimeter

The professional's choice for both HVAC and electrical applications with a complete set of measurement features including dual displays that allow you to view amperage and voltage measurements simultaneously.

- Continuity buzzer
- Hold and maximum reading functions
- Auto ranging
- Auto power off and low battery indication
- Rubber over-molded case
- Frequency is measured by either jaws or test leads (ACD-10 PLUS only)
- Microamps for testing flame sensors (ACD-14 PLUS only)
- Diode test (ACD-14 PLUS only)

| FEATURES                | ACD-10 PLUS   | ACD-14 PLUS                  |
|-------------------------|---|------------------------------|
| True-RMS                | -   | -                            |
| AC Voltage              | 4.000 V, 40.00 V, 400.0 V, 600 V                          |                              |
| DC Voltage              | 400.0 mV, 4.000 V, 40.00 V, 400.0 V, 600 V                |                              |
| AC Current              | 40.00 A, 400.0 A, 600 A                                   |                              |
| Resistance              | 400.0 Ω, 4.000 kΩ, 40.00 kΩ, 400.0 kΩ, 4.000 MΩ, 40.00 MΩ |                              |
| Capacitance             | 500.0 nF, 5.000 μF, 50.00 μF, 500.0 μF, 3000 μF           |                              |
| Frequency               | 40 Hz → 400 Hz with Jaw, 10 Hz → 100 kHz with test leads  |                              |
| Temperature             | -   | -4°F → 999°F (-20°C → 537°C) |
| Dual Displays           | -   | •                            |
| Micro Amps              | -   | •                            |
| Accommodates Conductors | up to 1.0" (25 mm) in diameter                            |                              |

**INCLUDED ACCESSORIES:** Test leads, battery (installed), soft carrying pouch, K-type thermocouple with banana plug (ACD-14 PLUS only), user manual



ACD-10 PLUS

ACD-14 PLUS





**NEW  
2016**

## ACD-14-PRO Dual Display 600 A TRMS Clamp Multimeter

The ACD-14-PRO offers a complete range of measuring functions for both HVAC and electrical applications featuring a large backlit LCD dual display, capable of simultaneously displaying voltage and amps. The ACD-14-PRO includes TRMS, low pass filter, in-rush current, frequency, resistance, capacitance, temperature, DC micro amps, Amp-Tip and non-contact voltage detection. The Amp-Tip function allows for precise measurement of current down to the tenth of an amp for reliable, accurate current measurement of both large and small diameter wires. The low pass filter allows measurement of current and voltage on variable frequency drives (motors with speed controlled by frequency).

- Large LCD with dual display that can display voltage and amps concurrently
- True-RMS for accurate voltage measurements in noisy environments
- Low pass filter for current and voltage measurements on variable frequency drives
- Amp-Tip function for precise low current measurement down to 0.1 amp
- HVAC applications with temperature,
- DC micro-amps and capacitance In-rush current
- Temperature
- Non-contact voltage detection (NCV)
- Audible continuity and diode test
- Data hold
- Auto ranging
- Auto power off
- Low battery indicator
- Safety rated CAT III 600 V

| FEATURE   | ACD-14-PRO  |
|---|---|
| <b>AC Voltage</b><br>(Digital Low-Pass Filter, True-RMS)  | Range: 0.0 to 600.0 V, Accuracy: $\pm 1.0\% + 5\text{LSD}$ (50 to 60 Hz)  |
| <b>DC Voltage</b>   | Range: 0.0 to 600.0 V, Accuracy: $\pm 1.0\% + 5\text{LSD}$  |
| <b>AC Current (True-RMS)</b>  | Range: 0.00 to 600.0 A, Accuracy: $\pm 1.8\% + 5\text{LSD}$ (50 to <100 Hz)<br>$\pm 2.0\% + 5\text{LSD}$ (100 to 400 Hz)  |
| <b>Precise Low Current AC</b><br>(Amp-Tip)  | Range: 0.00 to 60.00 A, Accuracy: $\pm 1.5\% + 5\text{LSD}$ (50 to 60 Hz)   |
| <b>DC Micro amps</b>  | Range: 0.0 to 2000 $\mu\text{A}$ , Accuracy: $\pm 1.0\% + 5\text{LSD}$  |
| <b>Capacitance</b>  | Range: 200.0 $\mu\text{F}$ , 2500 $\mu\text{F}$ , Accuracy: $\pm (2.0\% + 4\text{LSD})$   |
| <b>Diode Test</b>   | Range: 0.0 to 3.000 V, Accuracy: $\pm (1.5\% + 5\text{LSD})$  |
| <b>Temperature*</b><br>(Type K thermocouple)<br>*K-type thermocouple accuracy tolerances not included | Range: -40.0 to 752 $^{\circ}\text{F}$ , -40.0 to 400 $^{\circ}\text{C}$ , Accuracy: $\pm 1.0\% + 1.5\text{ }^{\circ}\text{F}$ (-40.0 to 99.9 $^{\circ}\text{F}$ )<br>$\pm 1.0\% + 2\text{ }^{\circ}\text{F}$ (100 to 752 $^{\circ}\text{F}$ )<br>$\pm 1.0\% + 0.8\text{ }^{\circ}\text{C}$ (-40.0 to 99.9 $^{\circ}\text{C}$ )<br>$\pm 1.0\% + 1\text{ }^{\circ}\text{C}$ (100 to 400 $^{\circ}\text{C}$ ) |
| <b>Non-Contact Voltage</b>  | •   |
| <b>Backlight</b>  | •   |
| <b>Auto Power Off</b>   | •   |

**INCLUDED ACCESSORIES:** User manual, Test leads, Carrying case, Batteries AAA (2), Banana plug K-type thermocouple



**ACD-14-PRO Dual Display  
600 A TRMS Clamp Multimeter**

**Clamp Meters**

## ACDC-3400 IND AC/DC CAT IV Industrial Clamp Meter

If an industrial or utility testing application demands a higher level of safety, reach for this CAT IV rated Clamp Meter.

- Extra large jaws accommodate wide wires
- True-RMS for accuracy and dependability
- Peak hold
- Auto and manual ranging
- Auto power off
- Data hold
- Backlight
- Diode test
- MAX/MIN recording
- Audible continuity

| FEATURE                        | ACDC-3400 IND   |
|--------------------------------|---|
| <b>True-RMS</b>                | •   |
| <b>DC Voltage</b>              | 660.0 mV, 6.600 V, 66.00 V, 660.0 V, 1000 V   |
| <b>AC Voltage</b>              | 660.0 mV, 6.600 V, 66.00 V, 660.0 V, 750 V  |
| <b>AC Current</b>              | 66.00 A, 660.0 A, 1000 A  |
| <b>DC Current</b>              | 660.0 A, 1000 A   |
| <b>Resistance</b>              | 660.0 $\Omega$ , 6.600 k $\Omega$ , 66.00 k $\Omega$ , 660.0 k $\Omega$ , 6.600 M $\Omega$ , 66.00 M $\Omega$ |
| <b>Capacitance</b>             | 6.600 nF, 66.00 nF, 660.0 nF, 6.600 $\mu\text{F}$ , 66.00 $\mu\text{F}$ , 660.0 $\mu\text{F}$ , 6.6 mF        |
| <b>Frequency</b>               | 66.00 Hz, 660.0 Hz, 6.600 kHz, 66.00 kHz, 660.0 kHz, 1.000 MHz  |
| <b>Continuity</b>              | •   |
| <b>Accommodates Conductors</b> | Up to 2.0" (51 mm) in diameter  |

**INCLUDED ACCESSORIES:** Deluxe carrying case, test leads, test leads, battery (installed), user manual.



**ACDC-3400 IND**

★★★★★  
Rated 4.3 Out of 5 Stars

### Recommended Accessories

**FOR: ACDC-3400  
TL35B  
Test Leads**  
(See Page 56)



## RS-1007 PRO CAT IV Analog Clamp Meter

Take these clamp meters to extremes. Digital clamp meters have LCD screens that tend to freeze below 32°F (0°C), but the Amprobe analog clamp meters can take extreme heat or cold and keep on measuring amps and volts without problems or batteries.

- Easy-to-read rotary scale
- Works in temperatures from 5°F to 122°F
- Does not need batteries to measure volts or amps
- Operates on 50Hz and 60Hz frequencies
- Pointer lock - data hold



RS-1007 PRO

| FEATURE                 | RS-1007 PRO                      |
|-------------------------|----------------------------------|
| AC Voltage              | 150 V, 300 V, 600 V              |
| AC Current              | 15 A, 40 A, 100 A, 300 A, 1000 A |
| Resistance              | 1000 Ω                           |
| Continuity              | •                                |
| Accommodates Conductors | up to 1.88" (47 mm) in diameter  |

**INCLUDED ACCESSORIES:** Test leads, battery (installed, for resistance measurement only), user manual, carrying case



AC50A



LH41A

## AC50A Leakage Current Clamp Multimeter

Great for applications requiring measurement of leakage and fault currents, this clamp measures low AC current down to microamps.

- Min/max control to see largest/smallest values in a series of measurements
- Relative value measurement to determine differentials
- Data hold to freeze measurement value on the display
- Digital display with analog bargraph
- Auto power off to save battery life
- Minimum resolution 0.01 mA

## LH41A AC/DC Low Current Clamp Meter

This highly accurate leakage clamp takes precise low-current measurements with 1mA resolution up to 4A; 10mA resolution from 4A to 40A

- Data hold
- Auto power off
- Auto zero button to zero display for DC
- Excellent accuracy and resolution

| FEATURE                 | AC50A  | LH41A                           |
|-------------------------|--|---------------------------------|
| AC Voltage              | 400.0 V                                      | -                               |
| AC Current              | 40.00 mA, 400.0 mA, 4.000 A, 40.00 A, 60.0 A | 4.000 A, 40.00 A                |
| DC Current              | -  | 4.000 A, 40.00 A                |
| Resistance              | 400 Ω  | -                               |
| Continuity              | •  | -                               |
| Accommodates Conductors | up to 1.2" (30 mm) in diameter               | up to 0.78" (20 mm) in diameter |

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, test leads (AC50A only), carrying case (AC50A only)

AC50A



ACD-6 PRO

## ACD-6 PRO Digital Clamp Meter

This high-current clamp doubles as a multimeter for AC and DC voltage, resistance and continuity.

- Auto and manual ranging
- Relative zero mode
- Auto power off
- Data hold
- Diode test
- Audible continuity

| MEASUREMENTS            | ACD-6 PRO   | BEST ACCURACY |
|-------------------------|---|---------------|
| DC Voltage              | 400.0 mV, 4.000 V, 40.00 V, 400.0 V, 600 V                | 1.0% + 3 LSD  |
| AC Voltage              | 600 V   | 2.0% + 5 LSD  |
| AC Current              | 400.0 A, 1000 A   | 1.5% + 5 LSD  |
| Resistance              | 400.0 Ω, 4.000 kΩ, 40.00 kΩ, 400.0 kΩ, 4.000 MΩ, 40.00 MΩ | 1.0% + 4 LSD  |
| Accommodates Conductors | up to 1.77" (45 mm) in diameter                           | -             |

**INCLUDED ACCESSORIES:** Carrying case, batteries (installed), user manual



### Recommended Accessories

- RS-1007 PRO, ACD-6 PRO
- TL35B Test Leads (See Page 56)
- ACD-6 PRO ELS2A AC Line Splitter (See Page 56)



## EL52A AC Line Splitter

Measure the current on a 2-wire or 3-wire power cord up to 15 A without having to cut off the plug and separate the conductors, or open electrical boxes on 120 V lines. Use with any Amprobe clamp meter.

- Two measurement loops, 1X and 10X for increased sensitivity
- Built-in voltage measurement jacks to check for voltage sags and surges
- Rated for 120 V, 15 Amps



EL52A



# Digital Multimeters

With Amprobe's broad selection of digital multimeters, you can find the perfect match for any job. From industrial meters safety-rated for CAT IV electrical environments, to simple pocket-sized meters, you'll find a digital multimeter that fits your needs.



**TOP RATED**

**5 Out of 5 Stars**

See The Top Rated AM-500 Series Digital Multimeters



# Digital Multimeter Selection Guide

Rugged, high performance multimeters for troubleshooting any application

| MODEL:                    | AM-510                                       |               | AM-530       |                                  | AM-570       |                                | 37XR-A        |                                | 38XR-A                       |                            | HD110C       |              | HD160C       |              | AM-500       |              | DM73C        |              | PM51A        |              | PM55A        |              |              |
|---------------------------|--|---------------|--------------|----------------------------------|--------------|--------------------------------|---------------|--------------------------------|------------------------------|----------------------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|
|                           | PG 13  | PG 13         | PG 13        | PG 14                            | PG 14        | PG 15                          | PG 15         | PG 16                          | PG 16                        | PG 16                      | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        | PG 16        |              |
|                           | Professional Autoranging Digital Multimeters |               |              | XR Full-Size Digital Multimeters |              | Heavy Duty Digital Multimeters |               | Autoranging Digital Multimeter | Pen-style Digital Multimeter | Pocket Digital Multimeters |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Safety Rating             | CAT III 600 V                                | CAT III 600 V | CAT IV 600 V | CAT III 600 V                    | CAT IV 600 V | CAT IV 1000 V                  | CAT IV 1000 V | CAT III 600 V                  | CAT II 600 V                 | CAT II 600 V               | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V | CAT II 600 V |
| True-RMS                  |  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| AC Voltage (V)            | 600 V  | 600 V         | 1000 V       | 750 V                            | 750 V        | 1000 V                         | 1000 V        | 600 V                          | 600 V                        | 600 V                      | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        |
| DC Voltage (V)            | 600 V  | 600 V         | 1000 V       | 1000 V                           | 1000 V       | 1500 V                         | 1500 V        | 600 V                          | 600 V                        | 600 V                      | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        | 600 V        |
| AC Current (A)            | 10 A   | 10 A          | 10 A         | 10 A                             | 10 A         | 2 A                            | 2 A           | 10 A                           |                              |                            |              |              |              |              |              |              |              |              |              |              |              | 2000 µA      |              |
| DC Current (A)            | 10 A   | 10 A          | 10 A         | 10 A                             | 10 A         | 2 A                            | 2 A           | 10 A                           |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              | 2000 µA      |
| Microamps                 | •  | •             | •            | •                                | •            |                                | •             | •                              |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              | •            |
| Resistance                | •  | •             | •            | •                                | •            | •                              | •             | •                              |                              |                            |              |              |              |              |              |              |              |              |              | •            |              |              | •            |
| Capacitance               | •  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              | •            |              |              |              | •            |
| Inductance                |  |               |              | •                                |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Frequency                 | •  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              | •            |              | •            |
| Duty Cycle                | •  |               | •            | •                                | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Relative Zero             | •  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Temperature Inputs        |  | 1             | 2            |                                  | 1            |                                | 1             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Diode Test                | •  | •             | •            | •                                | •            | •                              |               | •                              | •                            | •                          | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            |
| Continuity Beeper         | •  | •             | •            | •                                | •            | •                              | •             | •                              | •                            | •                          | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            |
| Non-Contact Voltage       | •  | •             | •            |                                  |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              | •            |
| Logic Test                |  |               |              | •                                |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Autoranging               | •  | •             | •            | •                                | •            |                                | •             | •                              | •                            | •                          | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            |
| Battery Test              | •  |               |              |                                  |              |                                |               | •                              |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| DC Loop Current 4-20m A   |  |               |              |                                  | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| dBm Reading               |  |               |              | •                                | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Backlight                 | •  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Bar Graph                 |  | •             | •            | •                                | •            |                                | •             |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Data Hold                 | •  | •             | •            | •                                | •            | •                              | •             | •                              | •                            | •                          | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            |
| Peak Hold (Crest)         |  |               | •            | •                                | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| AutoTest Function (V,A,R) |  |               |              |                                  |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              | •            |
| Data Logging              |  |               |              |                                  | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| PC Interface Capabilities |  |               |              |                                  | •            |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Auto Power Off            | •  | •             | •            | •                                | •            | •                              | •             | •                              | •                            | •                          | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            | •            |
| Work Light (LED)          | •  | •             | •            |                                  |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Low Pass Filter           |  |               | •            |                                  |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |
| Low Z                     |  |               | •            |                                  |              |                                |               |                                |                              |                            |              |              |              |              |              |              |              |              |              |              |              |              |              |

# AM-500 Series Digital Multimeters

Best-in-class autoranging, digital multimeters with features for residential, commercial electrical, industrial and HVAC applications. Features include True-RMS, dual thermocouples for measuring temperature differential, low impedance to detect stray voltage, low pass filter to accurately measure variable frequency drives and a built-in flashlight.

## AM-510 Commercial/Residential Multimeter

Designed for light commercial and advanced residential applications, the AM-510 enables you to re-wire an electrical panel, install light fixtures, troubleshoot home appliances, electrical sockets and automotive electrical issues.

- Voltage up to 600 V AC/DC, AC/DC current and resistance
- Frequency, capacitance and duty cycle
- VolTect™ non-contact voltage detection
- Audible continuity, diode test, backlit LCD display, data hold and relative zero mode

## AM-530 True-RMS Electrical Contractor Multimeter

Quickly troubleshoot voltage, perform repairs, run new wiring, check continuity on electrical connections, identify blown fuses, check motors or check transformers. The AM-530 is the perfect multimeter for the professional electrician.

- Voltage up to 600 V AC/DC, AC/DC current, resistance, frequency, capacitance, and temperature
- True-RMS
- VolTect™ non-contact voltage detection
- Audible continuity, diode test, backlit LCD display, data hold and relative zero mode

## AM-570 Industrial Multimeter

For professional electricians who need to maintain service or troubleshoot advanced electrical systems systems, the AM-570 is packed full of features such as True-RMS, dual thermocouples, a low impedance mode, and low pass filter to accurately take measurements on variable frequency drives.

- AC/DC Voltage up to 1000 V, AC/DC current, resistance, frequency, capacitance, temperature and duty cycle
- Low Z – to detect stray voltages
- Low pass filter for variable frequency drives
- VolTect™ non-contact voltage detection
- Audible continuity, diode test, backlit LCD display, data hold and relative zero mode



AM-570



AM-570

| Series Selection Guide                     |                     | AM-510           | AM-530            | AM-570                         |
|--|---------------------|------------------|-------------------|--------------------------------|
| <b>Application:</b>                        | <b>Feature:</b>     | <b>Res / Com</b> | <b>Electrical</b> | <b>Industrial</b>              |
| Safety Rating                              | Safety              | CAT III 600 V    | CAT III 600 V     | CAT IV 600 V<br>CAT III 1000 V |
| Measure voltage in noisy environments      | True-RMS            |                  | •                 | •                              |
| Electrical panels, AC outlets              | AC Voltage (V)      | 600 V            | 600 V             | 1000 V                         |
| DC systems, auto/marine batteries          | DC Voltage (V)      | 600 V            | 600 V             | 1000 V                         |
| AC Current - electrical panels, appliances | AC Current (A)      | 10 A             | 10 A              | 10 A                           |
| DC Current - electronics, DC motors        | DC Current (A)      | 10 A             | 10 A              | 10 A                           |
| Specified resistance and continuity        | Resistance (MOhms)  | 40 MΩ            | 40 MΩ             | 60 MΩ                          |
| Flame sensors                              | Microamps           | •                | •                 | •                              |
| Diodes in AC to DC converters              | Diode test          | •                | •                 | •                              |
| Fuses, light bulbs, wire connections       | Continuity          | •                | •                 | •                              |
| Household batteries                        | Battery test        | •                | -                 | -                              |
| Motor startup or run capacitors            | Capacitance         | •                | •                 | •                              |
| Frequency verification                     | Frequency           | •                | •                 | •                              |
| Non-contact voltage detection              | VolTect™            | •                | •                 | •                              |
| Electrical load-time on vs. time off       | Duty cycle          | •                | •                 | •                              |
| Temp of air vents, fuses, transformers     | Temperature inputs  | -                | 1                 | 2                              |
| Automatically selects measurement range    | Autoranging         | •                | •                 | •                              |
| Manually select measurement range          | Manual ranging      | •                | •                 | •                              |
| Voltage on variable frequency drives       | Low pass filter     | -                | -                 | -                              |
| Detect stray voltages                      | Low Z               | -                | -                 | -                              |
| Dimly lit areas                            | Built-in flashlight | •                | •                 | •                              |
| Meter resolution                           | LCD counts          | 4,000            | 4,000             | 6,000                          |
| Dimly lit areas                            | Backlight           | •                | •                 | •                              |
| Monitoring fast changing signals           | Bar graph           | -                | •                 | •                              |
| Two relative measurements on one screen    | Dual display        | -                | -                 | •                              |
| Data memory                                | Data hold           | •                | •                 | •                              |
| Difference between two measurements        | Relative reading    | •                | •                 | •                              |
| Max/min peak measurement                   | Max/min hold        | -                | •                 | •                              |
| Specialized signal measurements            | Peak hold (crest)   | -                | -                 | •                              |

**INCLUDED ACCESSORIES:** Test leads (pair), K-type thermocouple (AM-530, AM-570 only), batteries (installed), carrying case, user manual, temperature adaptor (AM-570 only)



AM-510, AM-530

AM-570

### Recommended Accessories


**DL248D**  
Deluxe Test Leads Kit (See Page 56)



**TPK-62**  
Temperature Adapter and 2 Thermocouples for AM-570 (Replacement part)



**TPK-59**  
Thermocouple (for AM-530)



## XR Series Multimeters

The XR Multimeter Series lets you customize features and functions for your electronic, electrical, plant maintenance or HVAC applications.

HVAC contractors and field service technicians have a choice of the manual ranging 37XR-A with capacitance or the autoranging, True-RMS 38XR-A with temperature and backlight.

For electronics troubleshooting, the True-RMS 37XR-A offers component and logic test. If you're an engineer, designing or troubleshooting industrial automation and control systems, check out the 38XR-A, a True-RMS multimeter with bright blue backlight and an optical PC interface.



38XR-A

- Autoranging
- Min/max and data hold
- Separate door for easy battery and fuse access
- Low battery indication
- Relative, peak, and average and data hold
- Analog bar graph
- Input warning tone when test leads are in wrong jack
- Auto power-off to save battery life

| FEATURE     | 37XR-A  | 38XR-A                         |
|-------------|---|--------------------------------|
| True-RMS    |   | •                              |
| DC Voltage  | 1.000 mV, 10.00 V, 100.0 V, 1000 V                                    |                                |
| AC Voltage  | 1.000 mV, 10.00 V, 100.0 V, 1000 V                                    |                                |
| DC Current  | 100.0 µA, 1.000 µA, 10.00 mA, 100.0 mA, 400.0 mA, 10.00 A             |                                |
| AC Current  | 100.0 µA, 1.000 µA, 10.00 mA, 100.0 mA, 400.0 mA, 10.00 A             |                                |
| Resistance  | 1000.0 Ω, 10.000 kΩ, 100.00 kΩ, 1000.0 kΩ, 10.00 MΩ, 40.00 MΩ         |                                |
| Continuity  |   | •                              |
| Diode       |   | •                              |
| Capacitance | 40.00 nF, 400.0 nF, 4.000 µF, 40.00 µF, 400.0 µF                      |                                |
| Frequency   | 100.00 Hz, 1.0000 kHz, 10.000 kHz, 100.00 kHz, 1.0000 MHz, 10.000 MHz |                                |
| Temperature | –   | -4°F → 2372°F (-20°C → 1300°C) |
| Duty cycle  | 0.00% → 90.0%   |                                |
| Logic test  | •   | –                              |
| Inductance  | 40 H  | –                              |
| dBm         | -13 dBm → + 50 dBm  |                                |

### Recommended Accessories

- DL248D** Deluxe Test Leads Kit (See Page 56)
- CT235A** Clamp Attachment
- CT237B** Clamp Attachment
- CT238A** Clamp Attachment (See Page 56)
- 38SW-A** RS232 Software/Cable (38XR-A DMM)
- USB-KIT3** Software kit 38XR-A (See Page 58)



DL248D



CT235A, CT237B, CT238A



38SW-A, USB-KIT3

**INCLUDED ACCESSORIES:** Magne-Grip™ holder with magnetic hanging strap, user manual, K-type thermocouple (38XR-A only), batteries (installed), test leads



38XR-A only

### ★★★★★ TOP RATED

**"WOW! Is This Thing Built!"** "I am a Electronic Field Tech and for this job you'd be hard pressed to find a finer DMM. The 37XR-A is the most rugged and feature packed meter I've owned. Having to carry everything I need in one kit, the 37XR-A does the job of several meters which means that I have less to carry. If you are looking for an accurate, tough, & do all True RMS DMM, this is the only meter you need.!"

- 38XR-A customer reviews



# HD110C and HD160C Heavy-duty Multimeters

Built for harsh environments, these unusually rugged meters offer extra features and superior protection that keep them operating reliably in heavy-duty applications. The meter's molded plastic case is made from flame-retardant thermoplastic to help protect against fire, chemicals, grease, falls, impacts, and abrasions.

- Measures up to 1500 V DC and 1000 V AC and withstands transients up to 12 kV (CAT IV 1000 V) – unmatched by other digital multimeters
- IP 67 rated and sealed to prevent dirt, grime and moisture from entering the case and causing inaccurate readings or damaging shorts
- Tough, fire-retardant thermoplastic resists grease and chemical spills and other environmental hazards
- All sensitive components are shock-mounted for drop resistance to at least eight feet
- Magne-Grip™ holder with magnetic hanging strap frees both hands for work
- Automatic polarity indication
- Superior 10,000 count resolution with bar graph
- Bright backlight for superior visibility
- Auto power-off to save batteries plus low battery indication



HD160C

| FEATURE       | HD110C  | HD160C  |
|---------------|---|---|
| True-RMS      | –   | •   |
| DC Voltage    | 200.0 mV, 2.000 V, 20.00 V, 200.0 V, 1500 V               | 1000.0 mV, 10.000 V, 100.00 V, 1500.0 V                               |
| AC Voltage    | 200.0 mV, 2.000 V, 20.00 V, 200.0 V, 1000 V               | 1000.0 mV, 10.000 V, 100.00 V, 1000.0 V                               |
| Current AC/DC | 200.0 µA, 2.000 mA, 20.00 mA, 200.0 mA, 2.000 A           | 100.00 µA, 1000.0 µA, 10.000 mA, 100.00 mA, 400.0 mA, 2.000 A         |
| Resistance    | 200.0 Ω, 2.000 kΩ, 20.00 kΩ, 200.0 kΩ, 2.000 MΩ, 20.00 MΩ | 1000.0 Ω, 10.00 kΩ, 100.00 kΩ, 1000.0 kΩ, 10.000 MΩ, 40.00 MΩ         |
| Diode         | •   | –   |
| Continuity    | •   | •   |
| Frequency     | –   | 100.00 Hz, 1000.0 Hz, 10.000 kHz, 100.00 kHz, 1000.0 kHz, 10.000 M Hz |
| Capacitance   | –   | 40.00 nF, 400.0 nF, 4.000 µF, 40.00 µF, 400.0 µF                      |
| Temperature   | –   | -4°F → 2372°F (-20°C → 1300°C)  |

**INCLUDED ACCESSORIES:** Test leads, batteries (installed), user manual, Magne-Grip™ holder with magnetic hanging strap, K-type thermocouple, threaded alligator clips



★★★★★  
**TOP RATED**  
"Great product with unlimited features"

"The HD160C-IP67 is a versatile instrument that allows me to carry just one instrument instead of several. Checking out panels, resistance and performing HVAC control wiring and trouble shooting, it is a hard instrument to beat. All of the electricians on my jobs and HVAC technicians carry the one versatile tester the Amprobe HD160C-IP67!"

- HD160C customer reviews

## Why You Need a True-RMS Reading Multimeter.

**Answer:** True-RMS instruments are accurate on any AC waveform. There are two basic AC measuring systems. One is "average sensing, RMS indicating." This is the most common system because it is affordable and easy to manufacture. An instrument with this type of measuring system measures the average of a sine wave, and then multiplies it by 1.112, allowing the instrument to indicate RMS. This measuring system is only accurate on sine waves.

The second measuring method is called "RMS Sensing, RMS Indicating." An instrument with this type of measuring system computes the RMS value of the measured waveform (sine or otherwise). This is referred to as "True-RMS" reading. This measuring system is accurate for any waveform. When an average sensing

instrument is used on a non-sinusoidal waveform, measurement accuracy could be off as much as 50%. Since you may not know what type of AC waveform you are measuring, a True-RMS instrument should be used whenever possible.



### Recommended Accessories

- DL248D** Deluxe Test Leads Kit (See Page 56)
- CT235A** Clamp Attachment
- CT237B** Clamp Attachment
- CT238A** Clamp Attachment (See Page 56)



DL248D



CT235A, CT237B, CT238A

## AM-500 Autoranging Multimeter

For residential or DIY applications. Install, troubleshoot or repair light fixtures, fans, appliances, or automotive electrical problems with the ease and safety of a CAT III 600 V rated product.



AM-500

- Autoranging feature automatically sets up voltage, current, and resistance ranges
- Voltage up to 600 V AC/DC
- Resistance
- Audible continuity
- Data hold
- Diode test
- Auto power-off

| FEATURE      | AM-500  | BEST ACCURACY   |
|--------------|---|---|
| AC Voltage   | 2.000 V, 20.00 V, 200.0 V, 600 V                            | ±(1.0% Rdg + 3 LSD) @ 45 Hz → 400 Hz, 2 V to 200 V ranges     |
| DC Voltage   | 200 mV, 2.000 V, 20.00 V, 200.0 V, 600 V                    | ±(0.8% Rdg + 1 LSD) @ 2 V → 200 V ranges                      |
| Resistance   | 200.0 Ω, 2.000 kΩ, 20.00 kΩ, 200.0 kΩ<br>2.000 MΩ, 20.00 MΩ | ±(1.0% Rdg + 2 LSD) @ 2 kΩ → 200 kΩ ranges                    |
| AC Current   | 200.0 μA, 2000 μA, 20.00 mA, 200.0 mA<br>2.000 A, 10.00 A   | ±(1.2% Rdg + 2 LSD) @ 200 μA to 200 mA ranges, 45 Hz → 400 Hz |
| DC Current   | 200.0 μA, 2000 μA, 20.00 mA, 200.0 mA<br>2.000 A, 10.00 A   | ±(1.0% Rdg + 2 LSD) @ 200 μA → 20 mA ranges                   |
| Battery Test | 1.5 V, 9 V  | ±(10% Rdg + 3 LSD)  |

**INCLUDED ACCESSORIES:** Test leads (pair), batteries (installed), carrying case, user manual



## DM73C Multimeter with Built-in Test Probe

Take one-handed measurements with this pocket-sized pen-style digital multimeter.

- Continuity beeper
- LCD display plus analog bar graph
- Auto power-off

| FEATURE    | DM73C   |
|------------|---|
| AC Voltage | 3.400 V, 34.00 V, 340.0 V, 600 V                          |
| DC Voltage | 3.400 V, 34.00 V, 340.0 V, 600 V                          |
| Resistance | 340.0 Ω, 3.400 kΩ, 34.00 kΩ, 340.0 kΩ, 3.400 MΩ, 34.00 MΩ |

**INCLUDED ACCESSORIES:** Test lead with alligator clip, 2 batteries (installed), spare tip, user manual



## PM Series Pocket Multimeters

Great things do come in small packages. Get innovative features, a full set of measurement functions and high safety ratings in an ultra-compact size. Only 3/8" (9.5 mm) thick, each meter weighs less than 3 oz (85 g).

- Easy, one-touch button control
- Oversize, easy-to-read digital display
- VolTect™ non-contact voltage detection (PM55A only)
- Automatically selects AC volts, DC volts or resistance, for convenience (PM55A only)
- Low Z input impedance detect ghost voltages
- Hi Z input impedance for electronic circuitry (PM55A only)
- Continuity beeper
- Diode test
- Data hold
- 30 ms high speed max hold
- Autoranging
- Auto power off

| FEATURE                                | PM51A   | PM55A   |
|--|---|---|
| AC/DC Voltage                          | 400.0 mV, 4.000 V, 40.00 V, 400.0 V, 600 V                | 6.000 V, 60.00 V, 600.0 V                       |
| AC/DC Current                          | –   | 400.0 μA, 2000 μA                               |
| Frequency                              | 400 Hz, 4 kHz, 40 kHz, 400 kHz, and 1 MHz                 | 10.00 Hz → 30.00 kHz                            |
| Resistance                             | 400.0 Ω, 4.000 kΩ, 40.00 kΩ, 400.0 kΩ, 4.000 MΩ, 40.00 MΩ | 600.0 Ω, 6.000 kΩ, 60.00 kΩ, 600.0 kΩ, 6.000 MΩ |
| Capacitance                            | 500.0 nF, 5.000 μF, 50.00 μF, 500.0 μF, 3000 μF           | 100.0 nF, 1000 nF, 10.00 μF, 100.0 μF           |
| VolTect™ Non-Contact Voltage Detection | –   | •   |

**INCLUDED ACCESSORIES:** Carrying case, battery (installed), user manual



DM73C



PM51A

PM55A





# Electrical Testers

## Don't second guess three-phase systems

The PRM-6 Phase Sequence and Motor Rotation Tester can test the motor rotation of 3-phase systems and verify 3-phase receptacle wiring and phase sequencing with test leads. An essential tool for motor rotation and phase sequence testing in commercial and industrial environments on electrical systems up to 700 V.

NEW  
2016



## INSP-3 Wiring Inspector

Verify in seconds whether a building's wiring complies with electrical code. Save time and money by testing more efficiently and identifying issues crucial to the safety and performance of an electrical system.

- Large display shows all relevant test data, no scrolling or switching screens needed
- Find faulty wiring that needs repair without removing outlet cover plates or panel covers, including:
  - Faulty splices and connections
  - Incorrect wiring
  - Undersized wiring
  - Faulty or incorrectly wired AFCIs/GFCIs
  - Incorrect line voltage
  - Poor ground quality
- Verify performance of electrical systems with user selectable 10, 15 and 20 amp loads
- Flashing screen clearly indicates incorrect wiring or voltage drop test failure
- Test without tripping circuit breakers or blowing fuses
- Check grounding for safety and ability to support sensitive electronic equipment



INSP-3

| FEATURE           | INSP-3  | BEST ACCURACY  |
|-------------------|---|----------------|
| Load              | Constant 10, 15 or 20 amp simulation regardless of line voltage | -              |
| Operating Voltage | 95 V AC → 140 V AC  | +/- 2% + 2 LSD |
| GFI Trip          | 6.0 mA nominal to trip GFI, 30 mA to trip RCD                   | -              |
| AFCI Trip         | Up to 8, 120 AMP pulses within 1/2 second period                | -              |

**INCLUDED ACCESSORIES:** Power cord, 9 V alkaline battery (installed), user manual, carrying case



LT-10

48" Antenna

## LT-10 Fluorescent Lamp Tester

Troubleshooting fluorescent lamps is as easy as 1-2-3, saving you valuable time and money. The Amprobe Fluorescent Lamp Tester is a problem solving tool designed to easily test whether fluorescent light bulbs and ballasts are working prior to installation or removal. The intuitive single button operation allows you to troubleshoot lamps and avoid wasteful disposal of fluorescent light bulbs and ballasts. The compact tool easily fits in your pocket and the industry leading 48" antenna makes it easy to test fluorescent bulbs while still in the fixture, often eliminating the need to stand on a ladder.

- Tests fluorescent (electroluminescent) lights
- Built-in VolTect™ non-contact voltage detection
- Filament pin test to check continuity of bulb
- Simple, one-handed, single button operation
- Ultra compact design for portability
- 48" removable, fully retractable antenna included to test lights and voltage without a ladder
- Compatible with all fluorescent light bulbs:
  - T2, T4, T5, T8, T9, T10, T12 fluorescent energy saving light bulbs

| FEATURE                                | LT-10  |
|--|--|
| Compatible lamps                       | T2, T4, T5, T8, T9, T10, T12 fluorescent energy saving light bulbs |
| Test voltage                           | Approximately 3 kV / 280 kHz                                       |
| Field strength                         | Approximately 100 μV/m at 260 - 300 kHz                            |
| Maximum antenna length                 | 48" (1.2 m)  |
| VolTect™ non-contact voltage detection | AC 90 V to AC 600 V, 50/60 Hz to CAT II 300 V, CAT I 600 V         |
| Filament pin test                      | T2, T4, T5, T8, T9, T10, T12                                       |

**INCLUDED ACCESSORIES:** 48" antenna, adaptor plate, user manual, battery and carrying case



# TIC 300 PRO High Voltage Detector

Rugged and reliable for utility, industrial, heavy manufacturing and mine safety applications, the Amprobe TIC 300 PRO with VolTect™ detects voltages in low, medium and high voltage applications with bright visual and loud audible alerts.

- Utility tool for checking transmission lines, power distribution equipment, down power lines, fuses, and load break connectors
- Lower voltage setting for checking voltage presence in breaker panels, breakers, power outlets and wiring
- Verifies presence of voltage from 30 V AC to 122,000 V AC (122 kV)
- MSHA certified and intrinsically safe
- Push button functionality for ease of use with PPE gloves
- Visual and audible voltage indication
- Self-test verifies tester works properly
- Ergonomic design with a convenient handle
- Drop-proof to 6' (1.8 m)

| FEATURE                                | TIC 300 PRO   | TIC 410A     |
|--|---|--------------|
| VolTect™ Non-Contact Voltage Detection | 30 V AC → 1500 V AC<br>1500 V AC → 122,000 V AC (with Hot Stick TIC 410A) | –            |
| 48" length                             | –   | •            |
| Voltage                                |   | Up to 121 kV |

**INCLUDED ACCESSORIES:** CC-300 PRO carrying case, user manual, batteries (installed)



★★★★★  
**TOP RATED**

**"Easy to use, durable, affordable."**

*"Excellent product, works great under any conditions, very durable, can easily survive the occasional drop from the truck or bucket."*

*"This is a great replacement for the old tic tracers the line crews were using. The line crews love them! Great replacement for the money!"*

- TIC 300 PRO customer reviews



TIC 300 PRO

TIC 410A  
Hot Stick  
(Extends to 48")

## Is it Hot or Not?

### Why utility crews trust the Amprobe TIC 300 PRO

Feedback from a major US utility and the 30 underground crews who serve a North American city

In every truck, on every trouble call, there's one tool crews reach for first to ensure their safety: the TIC 300 PRO. It's the go-to tool for underground crews servicing secondary power lines for a large Northeastern US utility company. Approximately three hundred TIC PRO 300 tools are currently in use throughout their system.

The crew's work takes them down manholes under historic cities where the infrastructure is aging, and the problems are frequent. Whether they're working on 120 V, 240 V or 5 kV or greater, on cables, transformers, or switches, they begin each job by checking for live power with the TIC 300 PRO non-contact voltage detector. Every crew

carries at least one unit and they use it daily, often multiple times each day.

Lights flash and the TIC 300 PRO beeps with increasing frequency as it nears a source of electricity, leaving technicians no doubt whether the source is live or not.

The crews like how simple the TIC 300 PRO is to use even with heavy gloves and full PPE on. They push one button to turn the unit on, another to select low or high range setting. After two decades of using TIC product line, the crews know it, trust it, and feel safe – it is exactly what they need.

### Recommended Accessories

**TIC 410A Hot Stick for the TIC 300 PRO**  
Safely check voltages up to 122 kV with this 48" Hot Stick and the TIC 300 PRO.



**CC-300 PRO Carrying Case**  
(Replacement part)



NEW  
2016



PRM-6

## PRM-6 Phase Sequence and Motor Rotation Tester

The PRM-6 Phase Sequence and Motor Rotation Tester can test the motor rotation of 3-phase systems and verify 3-phase receptacle wiring and phase sequencing with test leads. An additional advanced feature is wireless motor rotation detection, which senses motor rotation direction without use of test leads, particularly useful for fast-running motors when the motor rotation cannot be visually determined or when the drive shaft is not visible. The PRM-6 is an essential tool for motor rotation and phase sequence testing in commercial and industrial environments on electrical systems up to 700 V.

- 3-phase wire sequence indication
- Synchronous or asynchronous motor rotation direction
- Error displays (missing phase, one input connected to neutral or PE)
- Non-contact, wireless motor rotation detection on running motors
- Indicates motor rotation of disconnected motors when spinning the shaft by hand or other means
- 3-phase to phase voltage up to 700 V
- Clear backlit LCD display with easy to read symbols
- Durable, rubber casing for 3 ft. (1 m) drop-proof protection
- Safety: CAT IV 600 V

| FEATURE  | PRM-6   |
|--|---|
| 3-Phase indication and open-phase check        | LCD   |
| Phase rotation detection                       | Voltage range (frequency):<br>40 – 700 V (16 – 60 Hz)<br>50 – 700 V (60 – 400 Hz)<br>Nominal test current: < 3.5 mA |
| Non-contact, wireless motor rotation detection | Frequency range: 16 – 400 Hz  |
| De-energized motor rotation test               | Voltage range: ≥ 1 V – 700 V<br>Frequency range: 2 – 400 Hz   |

**INCLUDED ACCESSORIES:** 3 test leads, 3 test probes, 3 alligator clips, user manual, carrying bag, 2 AAA batteries



### Recommended Part

**TL-PRM-6**  
Replacement  
Test Lead Set



## MO-100 Milliohmmeter

Spot potential failures fast with the portable, battery powered MO-100. Check for opens or shorts in motor windings, generators and transformers. Test heating elements and wire-to-wire resistance in critical electrical connections.

- Accurate four terminal measurement down to 100  $\mu\Omega$  without test leads resistance compensation
- Three test currents with over-temperature protection for measurement precision
- Protection against inadvertent connection to overvoltage
- Potential lead resistance, current lead resistance checks
- Indicates measurement errors due to temperature or connection problems
- Auto-hold and auto-off features
- Lightweight, robust and compact
- "O-Ring" sealed enclosure

| FEATURE          | MO-100  |
|------------------|---|
| Measuring Ranges | 0 – 200.0 m $\Omega$ in steps of 100 $\mu\Omega$<br>0 – 2000 m $\Omega$ in steps of 1 m $\Omega$<br>0 – 20.00 $\Omega$ in steps of 10 m $\Omega$<br>0 – 200.0 $\Omega$ in steps of 100 m $\Omega$<br>0 – 2000 $\Omega$ in steps of 1 $\Omega$ |
| Test Current     | 1 mA (2000 $\Omega$ range)<br>10 mA (20 $\Omega$ / 200 $\Omega$ ranges)<br>100 mA (200 m $\Omega$ / 2000 m $\Omega$ ranges)   |

**INCLUDED ACCESSORIES:** User manual, test leads, batteries (installed)




MO-100

9.8" (L) x 7.5" (W) x 4.3" (D)  
(250 mm x 190 mm x 110 mm)

### Recommended Part

**MO-100-LEADS**  
Replacement  
Test Leads



## VP-1000SB

Designed for safe and convenient, non-contact AC voltage detection without interruption to electrical systems, the VP-1000SB provides 3-way visual, audible and vibration alerts when AC voltage is present.

- Designed to discern between hot and neutral wires up to CAT IV 1000 V AC
- Safety rated for indoor and outdoor applications
- Test for AC voltage cables, circuit breakers, wall sockets, junction boxes, and fuses

| FEATURE              | VP-1000SB                  |
|----------------------|----------------------------|
| AC Voltage Detection | 90 → 1000 V AC             |
| Indicator            | Lights, Beeps and Vibrates |
| Safety Rating        | CAT IV 1000 V              |

**INCLUDED ACCESSORIES:**  
User manual, batteries (installed)



VP-1000SB

## VP-440 Non-contact Volt Probe®

Designed for safe, non-contact voltage detection, this voltage probe doesn't require much budget or demand much space. It fits conveniently in a shirt pocket, tool belt or pouch.

- Safely check for AC voltages without disconnecting the electrical loads
- Test cables, circuit breakers, wall sockets, junction boxes, and fuses
- Completely insulated, with no exposed metal or conductive parts
- No current flow is needed for correct operation

| FEATURES             | VP-440         |
|----------------------|----------------|
| AC Voltage Detection | 100 V → 1000 V |
| Indicator            | Lights         |
| Safety Rating        | CAT III 1000 V |

**INCLUDED ACCESSORIES:**  
User manual, batteries (installed)



VP-440

## ST-101B / ST-102B Socket Testers

Easily check and confirm proper wiring of electrical receptacles with the Amprobe ST-101B and ST-102B Receptacle Testers. Quickly test sockets and confirm wiring and operation of AC outlets with the ST-101B and confirm that GFCI breakers are properly wired for protection with the ST-102B.

- Confirm proper wiring and operation of AC socket
- Easy-to-read lights indicate common wiring problems
- The trip test to confirm that GFCI protection is working properly (ST-102B only)
- For use on 110-125 V AC

| FEATURES   | ST-101B       | ST-102B       |
|------------|---------------|---------------|
| AC Voltage | 110 V → 125 V | 110 V → 125 V |
| GFCI       | -             | •             |



ST-101B



ST-102B

**INCLUDED ACCESSORIES:**  
Instruction sheet



ST-101B



ST-102B

## PK-110 Electrical Test Kit

Amprobe's PK-110 Electrical Test Kit offers three electrical testers with testing functions suitable for a variety of residential applications. The kit includes the AM-420 Digital Multimeter, ST-102B Socket Tester with GFCI and VP-1000 Non-Contact Voltage Detector. From identifying voltage presence in outlets and switches to confirming proper wiring of regular and GFCI protected outlets, the PK-110 kit boasts all the features needed to perform quick and safe electrical tests.



### AM-420 Digital Multimeter

- AC/DC voltage
- DC current
- Resistance
- Audible continuity and diode test
- Battery Test (1.5 V and 9 V)
- Data hold
- Safety rated: CAT II 250 V



### VP-1000 Non-Contact Voltage Detector

- AC voltage detection
- Visual voltage Presence alert
- Safety rated: CAT IV 1000 V



### ST-102B Socket Tester with GFCI

- Tests standard and GFCI outlets
- Verifies proper wiring
- Detects five different wiring faults
- CSA listed for safety



| FEATURE           | AM-420                               | VP-1000                      | ST-102B                    |
|-------------------|--------------------------------------|------------------------------|----------------------------|
| AC Voltage        | 200.0 / 250 V                        | –                            | –                          |
| DC Voltage        | 200 mV 2.000 / 20.00 / 200.0 / 250 V | –                            | –                          |
| Operating Voltage | –                                    | 90 Vac – 1000 V AC, 50/60 Hz | 110 – 125 V AC, 50 – 60 Hz |

**INCLUDED ACCESSORIES:** User manual, 9V battery, 2 AAA batteries



PY-1A

## PY-1A Voltage Tester

The PY-1A Voltage pocket-sized voltage tester detects AC and DC voltage ranges on cables, circuit breakers, wall sockets, junction boxes and other electrical wiring through direct contact.

- Neon lights indicate AC voltage at 120, 240, 277, 480 V and DC voltage at 160, 330, 380, and 600 V
- For use on energized or non-energized circuits
- Simple one hand operation, no buttons or setup required
- Test leads store conveniently in back of unit, properly spaced for outlet testing.
- CSA listed. Safety rated to European Standard 61010-01 Category III 600 V

| FEATURE    | PY-1A                      |
|------------|----------------------------|
| AC Voltage | 120 V, 240 V, 277 V, 480 V |
| DC Voltage | 160 V, 330 V, 380 V, 600 V |

**INCLUDED ACCESSORIES:** User manual



### ★★★★★ TOP RATED

*"Ease of operation and convenience"*

*"Easy to read voltage display, probe securing, and convenient size."*

- PY-1A customer reviews

## LAN-1 LAN Tester

With quick go/no-go tests, you can find opens, shorts and miswired cable installations. You can either step through the test cable one at a time, or let the unit automatically pulse through the pin-outs and display the results.

- Remote termination module tests installed cable on wall plate or patch panels
- Perform loopback or remote tests
- Buzzer sound warns for error condition in cable
- Two sets of LED lights indicate source and test
- Maximum line length: 328 yards (300 m)

| FEATURE                   | LAN-1  |
|---------------------------|--|
| Cable Types Tested        | 10/100 base-T; 10 base-2; RJ45; AT&T 258A; EIA / TIA 568A/568B; Token Ring |
| Continuity Maximum Length | > 300 meters   |
| Connector Types           | RJ45, BNC  |

**INCLUDED ACCESSORIES:** User manual, batteries (installed), remote terminator, RJ45 to female BNC cable, RJ45 to male BNC cable, RJ45 to RJ45 cable, Female BNC to Female BNC cable



LAN-1



### ★★★★★ TOP RATED

*"Ease of use"*

*"The tester was easy to use and worked very well in the field; it made the job a lot more easy. I recommend this tool for the field or home."*

- LAN-1 customer reviews

# Wire Tracers and Underground Locators

## Wire tracing reinvented.

With Amprobe's new AT-7000 wire tracer gives accurate results in minutes. New features and technologies simplify wire tracing and breaker identification. The Smart Sensor's™ patented sensor array and advanced signal processor provide instant feedback of wire location and direction on the large TFT LCD color display. Easily determine the direction and orientation of wires in walls, floors and ceilings up to 2 in/5 cm accuracy.



**TOP RATED**

**5 Out of 5 Stars**

See the Top Rated Advanced Wire Tracers



## AT-7000 Advanced Wire Tracer

Get accurate results in minutes with new features and technologies that simplify wire tracing and breaker identification. The Receiver's patented Smart Sensor™, with its innovative new antenna design and advanced signal processor, clearly displays the location and orientation of energized wires in walls, floors and ceilings on the large color TFT LCD screen. The powerful Transmitter utilizes two optimal frequencies for both energized and de-energized wire and breaker tracing, delivering consistently accurate results for novice users and experts alike. The new Scan and Locate feature clearly identifies the one correct breaker or fuse, eliminating the confusion from multiple false positive readings, common in older technology tracing tools.

- Traces wires in walls, ceilings, floors and corners
- Locates breakers and fuses
- Pinpoints shorts and opens
- High resolution 3.5" TFT LCD color display
- Three power modes
  - "High" power mode for normal circuits
  - "Low" power mode for precision tracing in difficult areas
  - "Clamp" power mode provides a boosted signal using signal clamp
- Two automatically selected frequency modes for optimal tracing on energized and de-energized circuits
- Signal booster rechargeable battery pack (BR-7000-T) increases transmitter signal strength
- Clamp-on attachment (SC-7000) for inducing signal into wires without access to bare conductors
- Embedded help screens make set-up easy and error free



AT-7000-R Receiver



AT-7000-T Transmitter



SC-7000 Signal Clamp

| Features                |   | AT-7020 | AT-7030 |
|-------------------------|---|---------|---------|
| Standard Features       | Traces energized and de-energized wires   | •       | •       |
|                         | Locates energized and de-energized breakers and fuses   | •       | •       |
|                         | Finds shorts and opens  | •       | •       |
|                         | Non-contact voltage detection   | •       | •       |
| Advanced Features       | Smart Sensor™ - wire position and direction indicator   | •       | •       |
|                         | "Scan and Locate" breaker finder  | •       | •       |
|                         | Two frequency modes for optimal tracing in energized (6 kHz) and de-energized (33 kHz) circuits | •       | •       |
|                         | Three power modes (high, low and clamp) for peak performance                                    | •       | •       |
|                         | High resolution 3.5" TFT LCD color display  | •       | •       |
|                         | Hot Stick attachment adapter  | •       | •       |
|                         | Signal Booster Li-Ion Rechargeable 7.2V Battery Pack  |         | •       |
| Signal clamp attachment |   | •       |         |

| KIT CONTAINS: |  | AT-7020    | AT-7030    |
|---------------|--|------------|------------|
| AT-7000-R     | Receiver unit with Smart Sensor, Tip Sensor and color TFT LCD display  | •          | •          |
| AT-7000-T     | Transmitter with two transmission frequencies (6 kHz and 33 kHz) and three power modes (high, low, clamp)                              | •          | •          |
| TL-7000       | Test Lead Set with alligator clips (Black & Red), 30 ft. grounding lead, power cord, plug adaptors and light socket adapter            | •          | •          |
| CC-7000       | Custom Amprobe hard carrying case that securely holds transmitter, receiver, signal clamp, test leads and accessories                  | •          | •          |
| SC-7000       | Signal Clamp accessory for inducing a signal into wires without access to bare conductors  | (optional) | •          |
| HS-1          | Three-way magnetic hanger for AT-7000-T transmitter, allowing for convenient hanging of unit, placement on belt or as a stand          | (optional) | •          |
| BR-7000-T     | Signal Booster Rechargeable Battery Pack (LI-ION, 7.2 V, 2.2 Ah), provides increased signal transmission power in High and Clamp modes | (optional) | •          |
| BR-7000C      | External battery charger for BR-7000-T   | (optional) | (optional) |

**INCLUDED ACCESSORIES:** Refer to the "Kit Contains" table above.



★★★★★  
**TOP RATED**  
"Great Tracer"

"I still have a lot to learn about this kit but am very satisfied with my purchase and it will be a very useful tool for years to come."

"This circuit breaker tracer works perfectly but you MUST follow the instructions. The unique auto-calibration system ensures that the correct breaker is identified every time without any false indications."

- AT-7000 customer reviews




AT-7020



AT-7030



★★★★★  
**TOP RATED**



### Tip Sensor

The shape of the tip sensor allows tracing in hard to reach areas, corners & tight spaces, as well as precise circuit breaker and fuse identification. By utilizing two different types of antennas (inductive coil and capacitive), the tip sensor enables optimal tracing results of both energized and de-energized circuits, which are automatically selected by operating mode.

### Smart Sensor™

Quickly and easily determine the precise direction and location of energized wires in walls, floors and ceilings with the patented Smart Sensor™. Combined with a fast signal processor that measures small changes in the detected signal multiple times per second, this new technology provides unmatched precision and ease of use for tracing energized wires.


### AT-7000-T Transmitter

Featuring three power modes high, low, and clamp, and two output frequencies (6kHz and 33 kHz), the AT-7000-T incorporates the best technologies available for optimal wire tracing and breaker identification on both energized and de-energized circuits. The AT-7000-T automatically sets the frequency based on detected voltage, and prompts users to set the power level based on their application. The color TFT LCD screen displays the detected voltage, frequency output and power mode.

## Quick and Easy Wire Tracing with the Smart Sensor™

### Tracing Wires in Walls, Ceilings and Floors

Tracing wires can be a challenge. The Amprobe AT-7000 makes tracing energized wires easier and more accurate than ever before. The Smart Sensor's™ patented sensor array and advanced signal processor provides instant feedback of wire location and direction on the large TFT LCD color display. Easily determine the direction and orientation of wires in walls, floors and ceilings up to 2 in/5 cm accuracy.



Large dynamic TFT LCD color display guides you in the direction and orientation of the energized wire.

Display shows when the Smart Sensor™ is centered over the location of the energized wire and indicates its precise direction and orientation.

## AT-3500 Underground Cable/Pipe Locator System

Keep productivity high and operational costs low, with the AT-3500. This rugged, economical solution helps you locate underground energized and de-energized wires, cables and pipes. Great for parking lot and airport lighting applications, it precisely pinpoints buried services, with exceptionally fast sound and meter response.

- Precisely pinpoint buried cables and wires
- Three testing modes for best accuracy:
  - Passive power (50 Hz / 60 Hz)
  - Passive radio (RF)
  - Active T-3500 signal generator with induction mode directly connected to the cable with test leads or optional clamp
- Proven 33 kHz frequency for most locating applications
- Avoid lines at utility construction sites with highly sensitive power and radio modes
- Take depth measurements up to 16' (4.9m)
- Backlit multiple-segment digital display with audible alerts to show and tell location of buried cables
- Semi-automatic gain control for fast signal location and control



AT-3500

### Recommended Accessories

- SC-3500** Signal Clamp
- MLS55-3** Pipe Transmitter






SC-3500

MLS55-3

| FEATURE                           | AT-3500   |
|-----------------------------------|---|
| Depth Measurement                 | 16 ft (4.9 m)   |
| Passive Tracing Frequencies       | 50 Hz / 60 Hz   |
| Transmitter Frequency             | Single, non-adjustable  |
| Receiver Active Frequencies (Hz)  | 32.768 kHz  |
| Receiver Passive Frequencies (Hz) | Range 1: radio 15 kHz to 23 kHz<br>Range 2: power network 50 Hz / 60 Hz; optionally 100 Hz (can be adjusted by Amprobe service personnel) |
| Receiver Depth Display Accuracy   | Range 1: radio +/- 20%<br>Range 2: power network +/- 20%<br>Range 3: transmitter +/- 5% (>5 m (6 ft), +/- 20% (<5 m (15 ft))              |
| Receiver Depth Range              | Maximum 16 ft (4.9 m)   |

**INCLUDED ACCESSORIES:** Receiver, transmitter, connection cables, ground stake, carrying case, user manual, batteries (installed)



### TOP RATED

**"Great for finding depth and location"**

"I've used one for years locating phone and gas lines and it works great. I can find and track wire or pipe and also know how deep within a few inches for digging and locating."

- AT-3500 customer reviews



## AT-4000-A Series Advanced Wire Tracer

Amprobe invented wire tracer technology decades ago and continues to set the standard today. The most advanced of all wire tracers, the AT-4000-A Series combines the technology, features and functions to make wire tracing fast and precise.

- One universal transmitter automatically switches to trace energized and non-energized (open, broken) wires
- Receiver is not position-sensitive - get accurate readings without rotating
- Locates breakers, neutrals, and ground lines
- Locates and traces wires in walls, floors, conduit, and computer cables
- Pinpoints shorts, ground faults and broken wires
- Performs tests without having to interrupt power
- Does not interfere with sensitive electronic equipment
- Precise sensitivity adjustment
- Battery booster strengthens signal for open tracing
- Clamp-on attachment injects signal for non-contact operation



AT-4005-A

| SPECS   | RANGE   |
|---|---|
| Transmitter operating voltage                 | 9 V - 300 V AC/DC   |
| Operating frequency                           | 32.786 kHz  |
| Receiver short mode range and open mode range | 20' (6 m) in air from the traced wire under test conditions |

| FEATURES   | AT-4001-A | AT-4004-A | AT-4005-A |
|--|-----------|-----------|-----------|
| Traces energized and de-energized wires  | •         | •         | •         |
| Locates energized and de-energized breakers and fuses                                | •         | •         | •         |
| Finds shorts and opens   | •         | •         | •         |
| Clamp-on attachment for inducing signal into wires without access to bare conductors | –         | •         | •         |
| Signal Booster 24V NiCad Rechargeable Battery Pack                                   | –         | –         | •         |

| KIT CONTAINS:                               | AT-4001-A    | AT-4004-A       | AT-4005-A       |
|---|--------------|-----------------|-----------------|
| Carrying Case                               | Soft SV-1000 | Hard CC-AT-4000 | Hard CC-AT-4000 |
| Receiver R-4000 CON                         | •            | •               | •               |
| Transmitter T-4000                          | •            | •               | •               |
| 110V Pigtail - Banana Plug Cord Set C2901   | •            | •               | •               |
| Alligator Clip - Banana Plug Cord Set C2902 | •            | •               | •               |
| Grounding Test Lead 25' (7.6 m) MTL-G       | •            | •               | •               |
| Alligator Clip for Ground Lead VRC-320      | •            | •               | •               |
| Clamp-on Transmitter Accessory A2202        | –            | •               | •               |
| Rechargeable Battery Pack B2024             | –            | –               | •               |
| Battery Pack Recharger B2025                | –            | –               | •               |
| User manual                                 | •            | •               | •               |

**INCLUDED ACCESSORIES:** Refer to the "Kit Contains" table above.

★★★★★  
**TOP RATED**

**"A must have for all electricians"**

*"This product will find wires buried in walls! Imagine being able to trace a circuit with a problem either from the receptacle device to where it has caused a problem or is discontinuous or shorted"*

*"With the AT-4004-A, I'm able to work in all situations with ONE unit! It's sensitive, easy to use, and with the optional clamp, it's easy to trace a conductor without the hassle of trying to find a suitable connection point."*

**- AT-4004-A customer reviews**

### Recommended Accessories

**A2202** Clamp-on Transmitter Accessory



## AT-2000-A Series Wire Tracers

Without interrupting power, you can trace live wires buried or hidden behind walls up to 13' (4 m) deep.

- Traces unenergized and open (broken) wires
- Locates breakers, neutral and ground lines
- Locates and traces wires in walls, floors, conduit, computer cables, etc.
- Pinpoints shorts, ground faults and broken wires
- Does not interfere with sensitive electronic equipment



AT-2005-A



AT-2004-A

| FEATURES   | AT-2004-A | AT-2005-A |
|--|-----------|-----------|
| Traces energized and de-energized wires  | •         | •         |
| Locates energized and de-energized breakers and fuses                                | •         | •         |
| Finds shorts and opens   | •         | •         |
| Clamp-on attachment for inducing signal into wires without access to bare conductors | •         | •         |
| Signal Booster 24V NiCad Rechargeable Battery Pack                                   | –         | •         |

| KIT CONTAINS:                                 | AT-2004-A | AT-2005-A |
|---|-----------|-----------|
| R-2000 Receiver                               | •         | •         |
| S2600-A Transmitter 9-300 V                   | •         | •         |
| T2200 Transmitter for open tracing            | •         | •         |
| Clamp-on Transmitter Accessory A2201CE        | •         | •         |
| B2024 Rechargeable Battery Pack               | –         | •         |
| B2025 Battery Pack Recharger                  | –         | •         |
| C2901 Cordset 110 Volt Plug to Banana Plugs   | •         | •         |
| C2902 Cordset Alligator Clips to Banana Plugs | •         | •         |
| User manual                                   | •         | •         |

**INCLUDED ACCESSORIES:** Refer to the "Kit Contains" table above.

## AT-1000 Wire Tracer

For basic applications where accuracy and routine troubleshooting are important, choose the Amprobe first-tier circuit tracer.

- Trace energized lines up to 300 V AC or V DC
- Trace unenergized and open conductors
- Identifies breakers and fuses without powering down
- Locates shorts
- Identifies wires in a bundle
- Identifies control, alarm and telephone system wiring
- Traces coaxial cable shield
- Receiver range 1 to 3 feet from a cable being traced



AT-1000

| FEATURE                                      | AT-1000                              |
|--|--------------------------------------|
| Trace energized lines up to 300 V AC or V DC | 100 V → 125 V AC (X1000 Transmitter) |
| Range 1-3' from a cable being traced         | R1000 Receiver                       |

**INCLUDED ACCESSORIES:** User manual, batteries (installed), transmitter, receiver, connection cables, carrying case



## CT-100 and CT-326-C Current Tracers

For tough industrial applications, we recommend these heavy-duty current instruments to trace live wires buried underground or hidden behind walls up to 4' (1.2 m) deep.

- Performs tests without having to interrupt power
- Locates breakers, neutral and ground lines
- Locates and traces wires in walls, floors, conduit, computer cables, etc.
- Pinpoints shorts and ground faults
- Does not interfere with sensitive electronic equipment

| FEATURES   | CT-100                            | CT-326-C                    |
|--|-----------------------------------|-----------------------------|
| Traces energized wires and locates breakers without interrupting power                         | 9 V → 300 V AC/DC                 | 9 V → 300 V AC/DC           |
| Traces non-energized wires (continuity and grounded wire) and pinpoints shorts & ground faults | T-100 Transmitter & 9 V batteries | Transmitter & 9 V batteries |
| Digital filter to assure accuracy in noisy industrial environments                             | -                                 | •                           |
| Sensitivity settings   | 3                                 | 12                          |

**INCLUDED ACCESSORIES:** User manual, transmitter, receiver, connection cables, carrying case

★★★★★  
**TOP RATED**

*"Product works fantastic!"*

*"...great at tracing circuits back to a panel board and identifying the correct one! Also makes picking the desired wire out of a pullbox full of options a breeze. I would recommend this unit highly!"*

- CT-100 customer review



CT-100



CT-326-C

## BT-250 Breaker Tracer

When you need to identify circuit breakers quickly and efficiently, count on this durable and dependable tracer.

- Works on all electrical systems from 90 to 250 V AC
- Meets the latest code requirement
- Automatic sensitivity adjustment
- Extremely accurate reading always finds the right breaker

| FEATURES        | BT-250        |
|-----------------|---------------|
| Voltage Range   | 90 V → 250 V  |
| Frequency Range | 40 Hz → 70 Hz |

**INCLUDED ACCESSORIES:** User manual, transmitter, receiver, carrying case, connection cable, light fixture adapter, batteries (installed)



BT-250



BT-250




## Safety Reference Guide

### International safety standards

Test equipment must be designed to protect people who work in the high-voltage, high-current environments. In order to prevent injury, the International Electrotechnical Commission (IEC) develops international general standards for safety of electrical equipment for measurement, control and laboratory use. The most current standard 61010 specifies overvoltage categories for electrical distribution systems. The category rating increases based on the closeness to the power source and a higher level of user protection that is required from test equipment.

### Proposed Energy Regions\*



\* Category ratings per IEC 61010-1  
Category boundaries may not be exact

# Power Quality Insulation Ground Resistance

Reduce downtime, predict equipment life and cut energy costs with Amprobe tools. The Amprobe insulation resistance testers support your preventative maintenance programs while the Amprobe power quality tools help you conserve energy and keep your equipment operating at peak performance. Use the Amprobe ground testers to not only operate efficiently, but also safely.



**TOP RATED**

See Amprobe's Top Rated Insulation  
/ Ground / Power Quality Testers



## AMB-45 Digital Insulation Tester

Test insulation of wires, cables, transformers and electrical motors quickly and easily with this rugged tester.



AMB-45

- Quickly test insulation of wires, cables, transformers and electrical motors
- Includes test leads and PC software
- Selectable test voltages 250 V, 500 V and 1000 V
- Programmable timer to perform the dielectric absorption ratio test
- Sensitive ohmmeter for checking resistance of motor windings
- Built-in voltmeter
- Data logging capabilities
- Download data to PC

| FEATURES                          | AMB-45                                |
|-----------------------------------|---------------------------------------|
| Insulation resistance (250 V DC)  | 4.000 MΩ, 40.00 MΩ, 400.0 MΩ, 4000 MΩ |
| Insulation resistance (500 V DC)  | 4.000 MΩ, 40.00 MΩ, 400.0 MΩ, 4000 MΩ |
| Insulation resistance (1000 V DC) | 4.000 MΩ, 40.00 MΩ, 400.0 MΩ, 4000 MΩ |
| Low resistance                    | 400.0 Ω, 4000 Ω                       |
| Voltage AC/DC                     | 600.0 V                               |

**INCLUDED ACCESSORIES:** Test leads, user manual, batteries (installed), carrying case, software & download cable



### Recommended Accessories

**AMB-45-CABLE** USB to 3.5mm Male Connector Communication Cable



★★★★★

### TOP RATED

*"very versatile and cost effective"*

*"As a generator sales and service company, it is imperative that we are able to perform testing of our customers generator windings. The Amprobe AMB-45 does this and much more in a cost effective platform. I would recommend this to companies such as ours."*

- AMB-45 customer review



AMB-25

## AMB-25 Digital Insulation Resistance Tester

Quality tools don't have to be expensive. This affordable, rugged megohmmeters is fast and easy to use, and offers features you need for most insulation test applications including wires, cables, transformers and motors.

- Selectable test voltages up to 1000 V
- Button lock for Dielectric Absorption Ratio (DAR) test
- Sensitive ohmmeter for checking resistance of motor windings
- Internal memory stores up to 9 readings

| FEATURES                          | AMB-25              |
|-----------------------------------|---------------------|
| Insulation resistance (250 V DC)  | 40.00 MΩ, 400.0 MΩ  |
| Insulation resistance (500 V DC)  | 400.0 MΩ, 1000.0 MΩ |
| Insulation resistance (1000 V DC) | 400.0 MΩ, 2000.0 MΩ |
| Low resistance                    | 999.9 Ω             |

**INCLUDED ACCESSORIES:** Test leads, user manual, batteries (installed)





# AMB-50, AMB-55 and AMB-110

## Industrial High Voltage Insulation Testers

Professional insulation diagnostics, automated calculations and step voltage testing satisfy the most demanding applications. Accurately test cables, transformers, motors, surge arrestors and generators in noisy environments such as high voltage switch yards. Built-in noise rejection filters and shielded test leads provide high EMI immunity.

- Use one tester for low and high voltage systems with selectable test voltages:
  - AMB-50: 500 V, 1000 V, 2500 V and 5000 V
  - AMB-55: 250 V to 5000 V with 25 V increments
  - AMB-110: 500 V to 10,000 V with 25 V increments
- R(t) graph plots resistance in real-time to illustrate a response to the applied voltage
- Programmable timer
- Automatic discharge of test object after measurement is complete
- Measure and display all parameters simultaneously on large LCD
- Fast charging and testing
- Dual power source: receptacle or rechargeable batteries (AMB-55 and AMB-110)
- Built-in memory stores up to 1000 measurements with time and date
- Record and manage measurement data with PC Software via either RS232 or USB



AMB-50



AMB-55



AMB-110

| FEATURE                                     | AMB-50   | AMB-55  | AMB-110       |
|---|--|---|---------------|
| Insulation Resistance                       | 0.5 MΩ → 20 GΩ,<br>2 MΩ → 40 GΩ,<br>5 MΩ → 100 GΩ,<br>100 MΩ → 1000 GΩ | 0 Ω → 999 kΩ,<br>1.00 Ω → 9.99 MΩ,<br>10.0 MΩ → 100.0 MΩ,<br>1.00 Ω → 9.99 GΩ   |               |
| Test Voltage and Step Voltage Display Range | 0 V → 5000 V   | 0 V → 5500 V  | 0 V → 10000 V |
| Current Display Range                       | 0 mA → 1.2 mA  | 0.00 nA → 9.99 nA, 10.0 nA → 99.9 nA,<br>100 nA → 999 nA, 1.00 μA → 9.99 μA, 10.0 μA → 99.9 μA,<br>100 μA → 999 μA, 1.00 mA → 5.50 mA |               |
| Dielectric Absorption Ratio (DAR)           | 0 → 9.99   | 0.01 → 100.0  |               |
| Polarization Index (PI)                     | 0 → 9.99   | 0 → 100.0   |               |
| Dielectric Discharge Test (DD)              | 0 → 9.99   | 0 → 100.0   |               |
| Leakage Current Display Range               | 1 mA → 1.2 mA  | 0 mA → 5.50 mA  |               |
| External Voltage Measurement                | 30 V → 600 V   | 0 V → 600 V   |               |
| Capacitance Measurement                     | –  | 0 nF → 99.9 nF, 100 nF → 999 nF, 1 μF → 50.0 μF   |               |
| Download PC Interface                       | •  |   | •             |
| Memory Size                                 | 18 Measurements  |   | 128 kB        |

**INCLUDED ACCESSORIES:** Test lead, large jaw alligator clips, batteries, user manual, carrying case, software, RS-232 cable (AMB-55, AMB-110 only), USB cable



AMB-50



AMB-55  
AMB-110



★★★★★  
**TOP RATED**  
**"All the required tests can be done with this product"**

*"Measurement of dielectric discharge has importance in the measurement of insulation resistance, it's really a diagnostic insulation tester."*

- AMB-110 customer reviews

### Recommended Accessories

#### AMB-50-KIT1

Test leads (AMB-50)  
(Replacement part)

#### AMB-KIT1

Test leads (AMB-55, AMB-110)  
(Replacement part)

#### AMB-KIT2

10 KV Shielded Lead with Tip  
(AMB-110 Replacement part)



AMB-50-KIT1

## AMB-3 Insulation Testers

Cut unscheduled downtime and reduce shock hazards. Quickly check the insulation resistance value of electric equipment and lines with this small, easy-to-operate tester.

- Sensitive ohmmeter for checking resistance of motor windings
- Built-in voltmeter
- Battery OK test
- Mirror scale
- Automatic discharge of equipment capacitance for safe removal of test leads



AMB-3

| FEATURE  | AMB-3         |
|--|---------------|
| Insulation Resistance with 500 V DC Test Voltage | 0 Ω → 1000 MΩ |
| Voltmeter  | 0 → 600 V AC  |

**INCLUDED ACCESSORIES:** User manual, batteries (installed), carrying case, test leads



**TOP RATED**

*"Best product on the market, job well done."*

*"Very easy to use and read, I would recommend this to anyone."*

- AMB-3 customer reviews



AMC-4

## AMC-2, AMC-3 and AMC-4 Hand-Cranked Insulation Testers

Test insulation of wires, cables, transformers and electrical motors without batteries or external power. With these hand-cranked tools, you're always ready to test.

- Sensitive ohmmeter for checking resistance of motor windings
- Guard terminal eliminates surface leakage that may influence readings
- Light and smooth operating crank
- Rugged cross coil movement
- High impact housing
- Spring-loaded terminal connection

| FEATURE   | AMC-2        | AMC-3        | AMC-4        |
|---|--------------|--------------|--------------|
| Insulation Resistance with 500 V DC Test Voltage  | 0 Ω → 100 MΩ | -            | 0 Ω → 100 MΩ |
| Insulation Resistance with 1000 V DC Test Voltage | -            | 0 Ω → 500 MΩ | 0 Ω → 500 MΩ |
| Low Resistance (5 V DC)                           | 0 Ω → 200 Ω  | 0 Ω → 200 Ω  | 0 Ω → 200 Ω  |

**INCLUDED ACCESSORIES:** User manual, carrying case, test leads



**TOP RATED**

*"This tool is a must."*

*"Great tool for the HVAC industry, has helped diagnose many troublesome compressors. Easy to use, and no batteries needed. Highly recommend it."*

- AMC-4 customer review

### Recommended Accessories

**AMC-LEADS** Test leads (AMC-2, AMC-3, AMC-4) (Replacement part)



## No Hassle Warranty

No waiting. No shipping charges.

Amprobe is committed to delivering the highest quality test and measurement products and provides a 1 year warranty with most products. The length of the product warranty is stated in the user's manual that comes with each product, which can be downloaded from [www.Amprobe.com](http://www.Amprobe.com).

To better serve you, in the unlikely event that an Amprobe product requires warranty service,

Amprobe authorizes over-the-counter product exchange from any authorized Amprobe distributor within 30 days from the date of purchase for products with a list price up to \$500. For products with a list price greater than \$500 or for issues encountered after the first 30 days but within the warranty period, please contact the Amprobe Service Department at **1-877-AMPROBE** for warranty services.

## GP-2A Ground Resistance & Resistivity Tester

For installation and troubleshooting, this instrument provides accurate and reliable measurements of ground resistance and soil resistivity to help you reduce power quality problems.

- Measures earth ground resistance with 3-point (fall of potential) or 2-point tests
- Calculates resistivity with 4-point test
- Automatic voltage measurement prevents false measurements
- Autoranging
- Store up to 999 measurements
- Create custom reports by downloading data to a PC

| FEATURE            | GP-2A            |
|--------------------|------------------|
| Ground Resistance  | 1999 $\Omega$    |
| Ground Resistivity | 314 k $\Omega$ m |
| AC Current         | -                |
| AC Voltage         | 0 V – 460 V      |

**INCLUDED ACCESSORIES:** User manual, batteries (installed), connection cables, 4 ground stakes, PC software and USB cable, carrying case



GP-2A

### Recommended Accessories

#### AMPRB-ET4

Set Earth Testing Accessory Kit  
(Replacement part)



## DGC-1000A Clamp-on Ground Resistance Tester

User-friendly and accurate, the DGC-1000A helps you work safely without test leads or auxiliary electrodes. The on-board memory and data logging features improve efficiency.

- Accurate ground resistance measurements from 0.025 to 1500 Ohms
- True-RMS current and leakage current measurements
- Accurate readings in less than 10 seconds
- Audible alert if continuity beep if the resistance is below 40 Ohms
- Data logging capability - 116 records
- Individual data point recordings
- User selectable high and low ohm audible alerts
- Auto power-off (can be disabled)
- Low battery indicator

| FEATURE            | DGC-1000A                                  |
|--------------------|--|
| Ground Resistance  | 0.025 $\Omega$ $\rightarrow$ 1500 $\Omega$ |
| Ground Resistivity | -  |
| AC Current         | 0.2 mA $\rightarrow$ 30.00 A               |
| AC Voltage         | -  |

**INCLUDED ACCESSORIES:** Carrying case, user manual, resistance calibration plate, batteries (installed)



DGC-1000A

### ★★★★★ TOP RATED

**"Great instrument. An advantage to have."**

*"On a motor grounding job where 800hp motors were failing on a continuous basis, we were able to pinpoint the lack of proper grounding that was causing harmonics and energizing armature shaft, to the point where it was reading 400v. On that job alone this tool proved invaluable and allowed the customer to save thousands on downtime and predictive maintenance. This tool will become a gem in your tool-bag just clamp it on and take live readings without breaking connections, I highly recommend it"*

- DGC-1000A customer reviews

## HVAC/R Solutions for Professionals



**A** Check AC Units

Check vent air flow and temperature

**B**



**C**

Check doors, windows and general drafts




**D**

Check general air quality



**E**

Check natural gas powered water heater/furnace



# Temperature

Turn to Amprobe for the tools you need as a HVAC/R, electrical, industrial maintenance, or automotive professional. We offer a complete line of temperature measurement tools, ranging from infrared to specialized thermometers that remotely capture readings.



**TOP RATED**

See the Top Rated IR-750 Infrared Thermometer



IR-750



IR-750

## IR-700 Series Infrared Thermometers

The Amprobe IR-700 Series Infrared Thermometers offer five IR thermometers with precision performance, unparalleled accuracy and response time. Specifically designed for HVAC/R, electrical, industrial maintenance, automotive as well as quality control and fire prevention applications.

- Distance to Spot ratio up to 50:1
- Wide temperature ranges
- Adjustable emissivity for measuring a variety of materials
- Min/max memory



|                                 | IR-708                         | IR-710                         | IR-720                             | IR-730                             | IR-750                             |
|---------------------------------|--------------------------------|--------------------------------|------------------------------------|------------------------------------|------------------------------------|
| Distance to Spot (D:S)          | 8:1                            | 10:1                           | 20:1                               | 30:1                               | 50:1                               |
| Temperature Range               | 0°F to 716°F<br>-18°C to 380°C | 0°F to 716°F<br>-18°C to 380°C | -26°F to 1922°F<br>-32°C to 1050°C | -26°F to 2282°F<br>-32°C to 1250°C | -58°F to 2822°F<br>-50°C to 1550°C |
| Best Accuracy                   | ±2% (Typical)                  | ±2% (Typical)                  | ±1.8% (Typical)                    |                                    |                                    |
| Emissivity                      | 0.95                           | 0.95                           | Adjustable from 0.10 to 1.00       |                                    |                                    |
| Display Resolution              | 0.1°C / 0.1°F                  |                                |                                    |                                    | 0.1°C / 0.1°F of reading < 999.9   |
| Backlit dual LCD display        | •                              | •                              | •                                  | •                                  | •                                  |
| Auto display and MIN/MAX Memory | •                              | •                              | •                                  | •                                  | •                                  |
| DIF/AVG Temperature Display     | -                              | -                              | •                                  | •                                  | •                                  |
| Tripod mount                    | -                              | -                              | •                                  | •                                  | •                                  |
| Programmable high and low alarm | -                              | -                              | -                                  | -                                  | •                                  |
| USB cable                       | -                              | -                              | -                                  | -                                  | •                                  |
| Built-in memory                 | -                              | -                              | -                                  | -                                  | 99                                 |
| K-type thermocouple measurement | -                              | -                              | -                                  | -                                  | •                                  |

**INCLUDED ACCESSORIES:** Battery (installed), user manual Carrying case: IR-720, IR-730, IR-750  
IR-750 only: K-type thermocouple, USB cable and software CD



### Recommended Accessories

**EPS-700** External Power Supply  
IR-750  
(Optional accessory)


★★★★★  
**TOP RATED**

*"Excellent high temperature IR probe"*

*"I needed an accurate probe that would give me the temperature of the molten iron we were producing in a chemical reaction. This has done very nicely for this task."*

- IR-750 customer reviews

100% of customers who reviewed this product also recommend it.



### Distance to Spot Ratio

The larger the Distance to Spot (D:S) ratio, the better the resolution and the smaller the area that can be measured. The IR-750 with a D:S of 50:1, will measure a 1" diameter at a distance of 50" away, perfect for demanding quality and process control applications.



## IR-450 Infrared Pocket Thermometer, Laser Pointer and Flashlight

A must have tool for everyday applications, the IR-450 3-in-1 Infrared Pocket Thermometer, Laser Pointer, and Flashlight offers a uniquely small and convenient form factor with professional 8:1 distance to spot ratio. More portable than traditional infrared thermometers, quickly check temperatures in HVAC/R, fire safety and protection, industrial maintenance, automotive and quality control applications.

- 8:1 Distance To Spot (D:S) ratio
- Bright laser pointer
- Built-in LED flashlight to illuminate dark areas
- Holds temperature reading (selectable °F/°C) for ten seconds

| SPECIFICATIONS        | IR-450                        |
|-----------------------|-------------------------------|
| Range                 | -22°F → 932°F (-30°C → 500°C) |
| Distance to Spot Size | 8:1 ratio                     |
| Best Resolution       | 0.5°F (0.2°C)                 |
| Best Accuracy         | +/- 4°F (2°C)                 |
| Emissivity            | Pre-set 0.95                  |

**INCLUDED ACCESSORIES:** Battery (installed), user manual, pocket clip



IR-450

## IR608A Infrared Thermometer with Laser Pointer

Point and press for quick and easy non-contact temperature measurement. Use this effective diagnostic tool to identify temperature for HVAC, fire safety and protection, industrial maintenance, automotive and quality control.

- Pocket-sized, ergonomic design
- Laser sighting for accurate targeting (CE EN60825 certified Class II)
- Display hold
- Fast response time
- Backlight display for visibility in a variety of working conditions
- Low battery indicator

| SPECIFICATIONS        | IR608A  |
|-----------------------|---|
| Range                 | 0°F → 750°F (-18°C → 400°C)                                   |
| Distance to Spot Size | 8:1 ratio   |
| Best Resolution       | 0.5°F (0.2°C)   |
| Best Accuracy         | +/- 2% of reading or +/- 3.5°F (+/- 2°C) whichever is greater |
| Emissivity            | Pre-set 0.95  |

**INCLUDED ACCESSORIES:** Battery (installed), user manual



IR608A

★★★★★  
**TOP RATED**

**"Excellent tool, and easy to use."**

*"This infrared thermometer is an excellent tool for on the job and at home to find heat loss at windows and doors. For use to detect heat loss and efficient use of energy. I would recommend this tool very highly to HVAC technicians and anybody that has to evaluate heat loss and efficient use of energy."*

- IR608A customer review

## THWD-3 and TH-3 Relative Humidity and Temperature Meters

An exceptionally wide ambient temperature range makes these meters versatile and accurate.

- Large LCD displays two measurements simultaneously
- Extended probe stem for easy access to air ducts
- Dew point and wet bulb (THWD-3 only)
- Min/max readings
- Temperature measurement range: -4°F (-20°C) to 140°F (60°C)
- Data hold
- Capacitive sensor with protective cover
- Auto power-off



THWD-3

**INCLUDED ACCESSORIES:** Carrying case, battery (installed), user manual

## TH-1 Compact Probe Style Relative Humidity Meter

Slip this little meter in your pocket and be ready for quick temperature and humidity checks.

- Displays relative humidity and temperature simultaneously
- Measure wet bulb and dew point
- Precision capacity relative humidity sensor with twistable protective cap
- Results in metric or English
- Stores min/max readings for comparisons
- Data hold



TH-1

| FEATURE                       | THWD-3                         | TH-3 | TH-1                            |
|-------------------------------|--------------------------------|------|---------------------------------|
| Temperature – Internal Sensor | -4°F → 140°F<br>(-20°C → 60°C) |      | -44°F → 122°F<br>(-20°C → 50°C) |
| Relative Humidity             | 5 → 95%                        |      | 10 → 95%                        |
| Dew Point Temp                | •                              | –    | •                               |
| Wet Bulb Temp                 | •                              | –    | •                               |



**INCLUDED ACCESSORIES:** Carrying case, user manual, battery



## THWD-5 Relative Humidity and Temperature Meter with Wet Bulb and Dew Point

Designed for HVAC technicians and plant maintenance engineers, this microprocessor-based psychrometer provides quick, easy access to wet bulb and dew point values as well as temperature and relative humidity.

- Extended probe for easy access to targets
- Large digital dual display with backlight makes readings easy-to-see
- Temperature with 0.1 degree resolution in °F or °C, front panel selectable
- Stores min/max measurements
- Data hold freezes last reading
- Tripod mountable



THWD-5

| FEATURES          | RANGE                                 | BEST ACCURACY   |
|-------------------|---------------------------------------|---|
| Relative Humidity | 0% → 100%                             | +/- 3% from 10% → 90% (at cal temp)<br>+/- 5% for other |
| Temperature       | 14°F → 140°F (-10°C → 60°C)           | +/- 0.6°C (+/- 1°F)                                     |
| Dew Point Temp    | -100.0°F → 139.8°F (-73.4°C → 59.9°C) | -   |
| Wet Bulb Temp     | 7.88°F → 139.8°F (-13.4°C → 59.9°C)   | -   |

**INCLUDED ACCESSORIES:** Carrying case, user manual, batteries (installed)





# TMD-56 Thermometer

The professional choice for HVAC technicians, electricians and research, industrial process, and quality control applications, this thermometer offers dual inputs for easy super-heat and sub-cool temperature measurements. Monitor and track temperatures, the multi-logging thermometer features real-time clocks with a calendar, user-selectable recording intervals, and easy data recall using up and down keys.

- °F/°C selectable
- Dual input: T1, T2, T1-T2
- Audible alert with Hi/Lo settings for out-of-range measurements
- Min/max with elapsed time, average, relative, hold functions
- Time and relative settings
- In-field thermocouple offset adjustment
- Robust holster protects the instrument
- Auto power-off saves batteries
- Download data to PC via USB
- Data capture: 256 samples with real-time data
- Data logging: 16 sets, maximum 16,000 data points
- Thermocouple offset adjustment
- Record, max, min, max-min, average, relative zero and hold functions
- Audible alerts with Hi/Lo setting
- Resolution 0.1°F/1°F (0.1°C/1°C)

| FEATURE  | TMD-56       | THERMOCOUPLE TYPE | TEMPERATURE RANGE                 |
|--|--------------|-------------------|-----------------------------------|
| Thermocouple Type                              | K            | K-TYPE            | -328°F → 2501°F (-200°C → 1372°C) |
| Basic Accuracy                                 | 0.05%        | J-TYPE            | -346°F → 2192°F (-210°C → 1200°C) |
| Number of Parameters on the Display            | 3            | T-TYPE            | -328°F → 752°F (-200°C → 400°C)   |
| Real Time Clock - Wireless Beeper with Setting | •            | E-TYPE            | -346°F → 1832°F (-210°C → 1000°C) |
| Data Capture                                   | 256 Samples  | R-TYPE            | 32°F → 3212°F (0°C → 1767°C)      |
| Data Logger                                    | 16000 Points | S-TYPE            | 32°F → 3212°F (0°C → 1767°C)      |
| PC Interface                                   | USB          | N-TYPE            | -58°F → 2372°F (-50°C → 1300°C)   |

**INCLUDED ACCESSORIES:** USB cable and software, user manual, 2 K-type thermocouples, batteries (installed)



TMD-56

Temperature

★★★★★  
**TOP RATED**

**"Great product"**

"Get a lot of use out of it, I'm a maintenance tech in a large paint shop and use it to check oven temps, I can log temps throughout the day and download on the computer. Great product with a lot of features."

**TMD-56**  
**Customer reviews**



## TR200-A Temperature and Relative Humidity Data Logger

One compact unit monitors both temperature and humidity and records it on your PC using the USB interface. Amprobe software included.

- Record sample interval timing, start/stop, date, time, Hi/Lo alarm threshold, and units
- Visible LED warnings alert you to air quality problems
- IP-65 rating for dust and moisture
- Wall mountable

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, PC software CD and USB cable



TR200-A

## TR300 Temperature and Relative Humidity Data Logger

Wall-mountable, self-standing, or tri-pod mountable, this data logger configures to your application.

- Temperature, relative humidity, dew point or web bulb measurements with real-time date/hour stamp
- Audible and visual alerts help you monitor IAQ conditions
- Stores up to 16,000 readings
- Records data to a PC with USB cable and Amprobe software included
- Programming on-screen or from the PC



TR300

| FEATURES                | TR200-A                        | TR300                          |
|-------------------------|--------------------------------|--------------------------------|
| Dual Display LCD        | -                              | •                              |
| Air Temperature Reading | 14°F → 140°F<br>(-10°C → 60°C) | -4°F → 158°F<br>(-20°C → 70°C) |
| Temperature Accuracy    | +/- 1°F (+/- 0.6°C)            | +/- 1°F (+/- 0.6°C)            |
| RH Reading              | 0.0 to 99.9%                   | 0 to 100%                      |
| RH Accuracy             | +/- 3% at 77°F (25°C)          | +/- 3% from 10 - 90%           |
| Recording               | 16000                          | 16000                          |
| Dew Point Reading       | -                              | •                              |
| On Screen Programmable  | -                              | •                              |
| Software Programmable   | •                              | •                              |

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, PC software CD and USB cable



# Environmental

High quality tools designed to save HVAC/R professionals time, money and keep buildings healthy. Amprobe offers a complete line of tools, designed specially for measuring environmental variables from simple one-time checks to advanced instruments that measure humidity and airflow, and check for gas leaks.

★★★★★  
**TOP RATED**  
See the Top Rated GSD600  
Gas Leak Detector



## MT-10 Moisture Meter

Measure the moisture content of wallboard, wood, mortar, plaster or other building materials to identify areas of water damage or harmful mold growth. Check wood or concrete flooring before installation, wood during drying or before woodworking.

- Three-color LED indicates moisture severity
- Backlight makes display visible in dim areas

**INCLUDED ACCESSORIES:** User manual, battery



MT-10



### TOP RATED

**"If you build quality, this is your tool."**

*"I watched the Amprobe MT-10 in action when my insurance adjuster came to check out ceiling damage. The rafters without visible water damage showed moisture, the insulation that needed replacing was quickly identifiable and the wall showed the path the water took to the next floor. Wow, this will save waiting to see mold or disintegration long before permanent damage."*

- MT-10 customer reviews

## TMA5 Mini Vane Anemometer

This pocket-sized tool gives you an easy way to measure air flow, temperature and humidity in the HVAC systems of residential, commercial or industrial buildings.

- Measures air velocity, temperature and ambient temperature (in °F or °C), humidity, dew point, wet bulb, wind chill
- Simple, two-button operation
- Selectable wind units: mph, ft/m, Knt, m/s, km/h, BF
- Maximum wind speed display
- Data hold
- Auto power-off with disable feature
- Low battery indication
- Ergonomic design with wrist strap
- External temperature probe included



TMA5

| FEATURE                    | TMA5  |
|----------------------------|---|
| Wind Speed Range           | 0.5 → 44.7 mph, 60 → 3937 ft/m, 0.4 → 38.8 knt, 1.1 → 20.0 m/s, 0.7 → 72.0 km/h, 1 → 8 BF |
| Air Temperature Range      | 32°F → 122°F (0°C → 50°C)   |
| External Temperature Range | -4°F → 158°F (-20°C → 70°C)   |
| Air RH% Range              | 5% → 95% RH   |
| Wind Speed Response        | averaging every 2 seconds   |
| Temperature Response Time  | 60 seconds (typical)  |
| Air RH% Response Time      | 60 seconds (typical)  |
| Wind-Chill Display         | •   |
| Dew Point Temperature      | •   |
| Wet Bulb Temperature       | •   |

**INCLUDED ACCESSORIES:** Battery (installed), user manual, external temperature probe, ergonomic wrist strap



### Recommended Accessories

**TPK-60** K-type external temperature probe



# TMA10A Anemometer with Flexible Precision Vane

The essential tool for HVAC technicians, the TMA10A measures air velocity or volume (CFM), plus temperature. Just enter surface area type for accurate airflow measurements.

- Large dual display for viewing airflow or velocity measurement including temperature
- Long flexible cord to access remote vanes
- Continuous moving average for up to 2 hours
- Air velocity average for up to 8 points
- Multi-point air flow (cfm) average
- PC interface for charting or analysis
- Min/max/average reading on a single point
- Data hold
- Auto power-off function

| FUNCTION                | RANGE                      | BEST ACCURACY        |
|-------------------------|----------------------------|----------------------|
| Air Velocity            | 0.40 → 25.00 m/s           | +/- 2% of full scale |
|                         | 125 → 4900 ft/min          | +/- 2% of full scale |
| Air Flow                | 0.01 → 99.99 m³/sec        | 0 → 9.999 m          |
|                         | 1 ft → 9999 cfm            | 0 → 9.999 ft         |
| Air Temperature °F (°C) | 32°F → 122°F (0°C to 50°C) | +/- 1.5°F (0.8°C)    |

**INCLUDED ACCESSORIES:** Carrying case, battery (installed), user manual, optional PC interface for charting or analysis



TMA10A



## TOP RATED

*"Does all that is asked of it! It is highly accurate and results are repeatable."*

- TMA10A customer review

### Recommended Accessories

**TM-SWA** USB Download Cable and Software CD  
(See Page 83)



# TMA40-A Anemometer, Relative Humidity and Temperature

With one tool, you can measure air velocity (FPM) or air volume (CFM), relative humidity, and temperature. Large digital display with backlight and flexible measurement vane makes measuring easier in difficult areas. Measures up to 99 points and logs up to 2400 measurements.

- Flexible measurement vane for accessing difficult areas
- Measures air velocity (fpm), air volume (cfm), relative humidity, and temperature
- Measure up to 99 points
- Data logging up to 2400 data points
- Optional PC interface for charting or analysis
- Large digital display with backlight

| FUNCTION          | RANGE                           | RESOLUTION         | ACCURACY             |
|-------------------|---------------------------------|--------------------|----------------------|
| Air Velocity      | 0.4 to 32 m/s (1.3 to 105 ft/s) | 0.1 m/s (0.1 ft/s) | +/- 3%               |
| Air Volume        | 0 → 99999 (cfm/cmm)             | 0.1 CMM - 1 CFM    | +/- 3%               |
| Temperature       | -4°F → 158°F (-20°C → 70°C)     | 0.1°F (0.1°C)      | ± 0.6°C (± 1°F)      |
| Relative Humidity | 0 → 100%                        | 0.1%               | +/- 3% @ 77°F (25°C) |

**INCLUDED ACCESSORIES:** Carrying case, battery (installed), user manual, optional PC interface for charting or analysis



TMA40-A



## TOP RATED

*"Great tool."*

*"The Amprobe TMA40-A is a great tool for air flow measurement. It does dew point, wet bulb, dry bulb, air speed, and air velocity. Great tool for troubleshooting duct problems."*

- TMA40-A customer reviews

### Recommended Accessories

**TM-SWA** USB Download Cable and Software CD  
(See Page 83)



## TMA-21HW Hot Wire Anemometer

Hot wire anemometer technology eliminates bearings and rotating parts to make these meters durable and measurements stable and accurate. It's the simple, safe way to monitor indoor air quality and measure air flow and temperature in residential, commercial and industrial air conditioning systems.



TMA-21HW

- 4' (1.2m) telescopic wand - no ladder needed for most commercial applications
- Measures air flow volume in CFM, CMM
- Instant average, 2/3 Vmax flow measurements
- Velocity m/s, ft/min, knots, km/hr, mph
- Relative humidity and temperature measurement
- Data hold, min/max with time stamp
- Data memory and real-time function (99 sets)
- 512KB auto data-logging capacity
- USB interface
- Wet bulb and dew point
- Large backlight LCD display shows five parameters

| FEATURE              | TMA-21HW  | BEST ACCURACY          |
|----------------------|---|------------------------|
| Air Flow             | 0.10 m/s → 30.00 m/s<br>0.2 km/hr → 110.0 km/hr<br>10 ft/min → 6000 ft/min<br>0.10 knots → 59.0 knots<br>0.12 MPH → 68.00 MPH | +/- 3% of rdg +/-1% FS |
| Air Flow Volume      | 0.000 CFM → 999900 CFM<br>0.000 CMM → 999900 CMM  | +/- 3%                 |
| Temperature          | -4°F → 140°F<br>(-20°C → 60°C)  | +/- 0.9°F (+/- 0.5°C)  |
| Relative Humidity    | 0.0 → 100%  | +/- 3%                 |
| Data-logging via USB | •   | -                      |
| Wet Bulb / Dew Point | •   | -                      |

**INCLUDED ACCESSORIES:** Batteries (installed), hard carrying case, user manual, USB cable and PC software



RLD-1

## RLD-1 Refrigerant Leak Detector

Troubleshoot air conditioning systems quickly and accurately with the RLD-1. State-of-the-art technology makes it easy to precisely pinpoint a wide variety of halogenated refrigerant leaks.

- Detects R-134a, R-404a, R-407c, R-410a, R-22, Freon and other refrigerants
- Sensitive gas sensor and advanced digital signal processing for high accuracy
- Built-in suction pump for precise sensor response
- Tri-color LED display and audio clearly indicate leaks
- High-Medium-Low (H/M/L) leak sensitivity selector
- Automatic zero and background compensation
- Low battery indication
- Ambient concentration reset

### Recommended Accessories

**RLD-1 SENSOR Replacement Sensor**  
(Replacement part)



| FEATURE                        | RLD-1                                       |
|--------------------------------|---|
| Detectable Gases               | R-134a, R-404a, R-407c, R-410a, R-22, Freon |
| R-22, 134a Sensitivity         | H - 3g/year, M - 15g/year, L - 30g/year     |
| R-404a, 407c, 410a Sensitivity | H - 4g/year, M - 20g/year, L - 40g/year     |
| Alarm Method                   | Buzzer, Tricolor LED bar Indicator          |
| Power Usage                    | 2 C size (3V DC) Alkaline Batteries         |
| Snake Tube Length              | 15.5" (40 cm)                               |

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, carrying case, leak check bottle, AC adapter



★★★★★

### TOP RATED

**"Best tool for the job!"**

*In over 25 years of business, I've seen units with suspected refrigerant leaks but were too small to find. With the Amprobe RLD-1 refrigerant leak detector I can take the guess work out of finding and repairing a refrigerant leak. I recommend that if you are in the HVAC business this is a must have for every tool bag!"*

- RLD-1 Customer reviews



## GSD600 Gas Leak Detector

Detect dangerous methane or propane leaks that can lead to explosions and gas poisoning. With its five-level LED and audible alarms, the GSD600 helps you assess whether the area is safe or needs to be vented. The frequency of the beeping increases with the concentration of the gas, allowing you to pinpoint the source of the leak in piping or appliances. The display provides an accurate measurement of the presence of gas in the area.

- Detects combustible gases
- Quickly identifies and pinpoints gas leaks for closed piping systems
- Automatic calibration feature level LED alarm: >40, >80, >160, >320, and >640 ppm
- Mute function and LED alerts for quiet areas
- Built-in earphone jack (earphones not included) for loud environments
- Flexible probe to access difficult measurement areas
- Auto power-off

| FEATURE     | RANGE            |
|-------------|------------------|
| Methane     | 40 ppm → 640 ppm |
| Propane     | 35 ppm → 580 ppm |
| Sensitivity | 35 ppm (propane) |

**INCLUDED ACCESSORIES:** Battery (installed), carrying case, user manual



GSD600

★★★★★  
**TOP RATED**

*"This thing really works."*

*"the Amprobe GSD600 found a leak at the furnace shut-off valve, I tightened nut and that was fixed."*

- GSD600 customer reviews

## Ultrasonic Leak Detectors

When leaks occur in pressurized systems, they emit an ultrasonic frequency humans can't hear. The ULD-300 and the TMULD-300 ultrasonic leak detectors convert the sounds into an audible range for fast, easy leak detection.

### ULD-300 Ultrasonic Leak Detector

Quickly locate gas leaks in pressurized air lines, steam lines, and refrigeration systems regardless of gas type (CFC, HFC, nitrogen and other non-combustible gases).

- Locates arcing in an electrical system
- Finds the ends of buried PVC pipes
- Parabola shield reduces background noise
- Access difficult or dangerous areas with extension tube

**INCLUDED ACCESSORIES:** Flexible tubing adapter, tubular extension, carrying case, power parabola, headphone, batteries (installed)



ULD-300

TMULD-300

### TMULD-300 Ultrasonic Leak Detector with Ultrasonic Transmitter

When leaking gases are not sufficiently pressurized, use the TMULD-300. It includes an ultrasonic transmitter that creates sound waves so you can check door or trunk seals for air tightness, or windshields for water tightness.

- Same features as ULD-300
- Transmitter "pressurizes" an area with ultrasonic sound

**INCLUDED ACCESSORIES:** Flexible tubing adapter, tubular extension, carrying case, power parabola, headphone, batteries (installed), UT-300 transmitter



ULD-300

★★★★★  
**TOP RATED**

*"Great product."*

*"This tool paid for itself many times over. I have found leaks large and small inside walls, on evaporator coils, condensers and water lines. I've loaned it to colleagues who purchased your product immediately after using mine. These tools lead the industry in leak detection through its sensitivity and ability to detect negative or positive pressure."*

- TMULD-300, customer reviews

#### Recommended Accessories

**UT-300** Ultrasonic Transmitter (ULD-300) (Replacement part)

**ULD-300-KIT1**  
Adapter Kit For ULD-300:  
TEA-1 Flexible tubing adapter  
PB-1 power parabola  
HP-1 headphone  
TE-1 tubular extension (Replacement part)



## CM-100 Carbon Monoxide Meter

This compact meter measures the presence of carbon monoxide and warns you when it exceeds safe levels.

- Alarm is preset to 25 ppm to warn about possible danger
- Adjustable CO warning levels: 25, 30, 35, 45, 50, 70, 100 and 200 ppm
- Backlight for viewing in dim areas
- Auto power-off to save batteries
- Self-test feature
- Dual digital backlit display

| FEATURE    | CM-100          |
|------------|-----------------|
| Range      | 0 ppm → 999 ppm |
| Resolution | 1 ppm           |

**INCLUDED ACCESSORIES:** User manual, batteries (installed)



CM-100

## CO2-100 Handheld Carbon Monoxide Meter

Get instant feedback on carbon dioxide levels up to 9,999 ppm, while you check the air quality compliance of hospitals, schools, offices, or production floors.

- Large, easy-to-read triple LCD display of CO<sub>2</sub>, temperature and relative humidity
- Selectable display of dew point and wet bulb
- High performance low-drift sensor designed with NDIR (Non-Dispersive Infrared) waveguide technology
- Backlight for working in dim areas
- TWA (time-weighted average) display for an 8-hour period
- 15 minutes STEL (short-term exposure limit) value
- Audible alarm threshold setting by carbon dioxide level
- Data hold, min/max, average functions
- Long term drift compensation for accurate readings

| FEATURE              | CO2-100   | CO2-200   |
|----------------------|---|---|
| CO <sub>2</sub>      | 0 → 9999 ppm  | 0 → 9999 ppm  |
| Temperature Range    | 14°F → 140°F (-10°C → 60°C)   | 14°F → 140°F (-10°C → 60°C)   |
| RH Range             | 0% → 95%  | 0% → 95%  |
| DP (Dew Point Temp.) | -4°F → 139.8°F (-20°C → 59.9°C)   | -4°F → 139.8°F (-20°C → 59.9°C)   |
| WB (Wet Bulb Temp.)  | 24.8°F → 139.8°F (-5.0°C → 59.9°C)  | 23°F → 139.8°F (-5.0°C → 59.9°C)  |
| Resolution           | 1 ppm - CO <sub>2</sub> concentration, 0.1°C / °F - Temp, 0.1%RH - Humidity | 1 ppm - CO <sub>2</sub> concentration, 0.1°C / °F - Temp, 0.1%RH - Humidity |

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, carrying case



CO2-100



CO2-200



### TOP RATED

**"Consistent calibration and fast updating."**

"I use this tool to check environmental CO<sub>2</sub> conditions in theaters and in the field. The range is good with humidity readings that went to 3% in Colorado sub-alpine desert and CO<sub>2</sub> readings that topped the 9,999 ppm limit in productions."

- CO<sub>2</sub>-100 customer reviews

## CO2-200 Wall-Mounted Carbon Monoxide Meter

Monitor critical, environmentally controlled areas such as laboratories and production facilities with this permanently mounted air quality meter.

- CO<sub>2</sub> measurements up to 9,999 ppm, temperature, relative humidity, dew point and wet bulb
- Audible alarm threshold setting for carbon dioxide levels with output drive relay to control air flow system
- High performance low drift sensor designed with NDIR (Non-Dispersive Infrared) waveguide technology with automatic background calibration
- Recording of min, max and average values with recall function
- Data hold

**INCLUDED ACCESSORIES:** Batteries (installed), carrying case, power adapter 110-240 V AC, user manual



CO2-200



## TACH-10 and TACH20 Combo Tachometers

Measure rotational speed of motors, conveyor belts and other moving or rotating systems with these handheld tachometers. The TACH20, our top-of-the-line tachometer includes six adapters, a surface speed wheel for contact RPM measurement and an infrared beam for non-contact measurements. The TACH-10 is an economical, universal tachometer that measures rotational and surface speed using both contact and non-contact methods.

- Built-in memory function automatically stores maximum, minimum and average values as well as the last measurement displayed
- Easy to select units and mode functions
- Select RPM using infrared beam or adapter: m/min, m/sec, ft/min, ft/sec, in/min, m, ft and in
- Auto power-off function

| FEATURE                 | TACH-10  | TACH20  |
|-------------------------|--|---|
| Rotation (Non-Contact)  | 10.0 rpm → 99999 rpm   | 1 min → 99999 min   |
| Rotation (Contact)      | 10.0 rpm → 19999 rpm   | 1 min → 19999 min   |
| Surface Speed (Contact) | 1.0000 → 9999.9 m/min<br>3.0000 → 30000 ft/min<br>1.0 → 10000 yd/min | 0.10 → 1999 m/min<br>0.40 → 6550 ft/min<br>4.00 → 78700 in/min<br>0.10 → 33.30 m/sec<br>0.10 → 109 ft/sec |

**INCLUDED ACCESSORIES:** Batteries (installed), user manual, reflective tape, carrying case, adapters



TACH-10



TACH20

## LM-100 and LM-120 Light Meters

These portable, easy-to-use digital light meters measure interior illumination levels from fluorescent, metal halide, high-pressure sodium or incandescent sources. Switch off, reduce or increase the output level of lighting fixtures. Reduce the energy burden of the building by significantly increasing the efficiency of its lighting system.

- Measure in lux or footcandles, front panel switchable
- Simple, one-handed operation
- Silicon photodiode sensor and filter for accuracy and high-resolution
- Analog DC voltage output to operate with chart recorder or data logger (LM-120 only)
- Zero adjustment (LM-120 only)
- Auto power-off to save battery life

| FEATURES            | LM-100  | LM-120             |
|---------------------|---|--------------------|
| Ranging             | Manual  | Automatic / Manual |
| Illumination Sensor | Silicon photodiode and filter   |                    |
| Range Lux           | 20, 200, 2000, 20000, 200000  |                    |
| Range Footcandles   | 20, 200, 2000, 20000  |                    |
| Calibration Point   | 2854 °K Cosine Angular corrected per JIS C 1609:1993 and CNS 5119 general A class |                    |
| Data                | Data hold   | Data hold, min/max |

**INCLUDED ACCESSORIES:** Batteries (installed), carrying case, user manual



LM-100

## LM-200LED Light Meter

This professional tester accurately measures light output of LED sources for all visible light ranges.

- Lux or footcandle measurement units, user selectable
- Data hold
- Max recording captures highest light measurement
- Measuring lights source include all visible ranges
- Accurate measurements with spectral response close to CIE luminous spectral efficiency
- Angled light cosine correction
- Extendable wire (approximately 5' (1.5 m))
- Measurements according to JISC1609:1993 and CNS 5119 general A class specifications

| FEATURE               | LM-200LED                       | BEST ACCURACY   |
|-----------------------|---------------------------------|---|
| LED Light Measurement | 200, 2000, 20000, 200000 lux    | +/- 3% (Calibrated to standard incandescent lamp 2856° K) and corrected LED day white-light spectrum. |
|                       | 20, 200, 2000, 20000 footcandle |   |

**INCLUDED ACCESSORIES:** User manual, battery (installed), carrying case



LM-200LED

## SM-10 and SM-20-A Sound Meters

These sound meters meet the measurement needs of safety engineers, health, industrial and safety offices as well as quality control. Use them to check compliance with safety regulations and perform acoustic analysis. They use two different weighting filters required by the IEC 651 and ANSI S1.4 Type 2 for audio filtering.

- A-weighting for general noise sound level
- C-weighting for measuring sound level of acoustic material control in various environments
- Display with 0.1dB steps on a 4-digit LCD
- Slow (1 sec) and fast (125ms) response settings to check peak and average noise levels
- PC interfaces (SM-20-A only)



SM-20-A

| FEATURES                           | SM-10  | SM-20-A       |
|------------------------------------|--|---------------|
| Microphone                         | 1/2" Electret condenser microphone                         |               |
| Standard Applied                   | IEC 651 Type 2, ANSI S1.4 Type 2                           |               |
| Dynamic Range                      | 50 dB  |               |
| Time Weighting                     | FAST (125 mS), SLOW (1 sec)                                |               |
| Frequency Range                    | 31.5 Hz → 8 kHz  |               |
| Measuring Level Range (Auto Range) | A-Weighting: 30 dB → 130 dB<br>C-Weighting: 35 dB → 130 dB |               |
| Data                               | Data hold  | Min/max       |
| Internal Memory                    | -  | 14000 records |

**INCLUDED ACCESSORIES:** Carrying case, user manual, battery (installed), USB cable download and software CD (SM-20-A only)



### ★★★★★ TOP RATED

"I work in a manufacturing plant and regularly check sound levels to make sure we are using the right hearing protection. We have been using the Amprobe SM-20-A Sound Meter for its ease of use and simple operations, and quick and easy testing. Love it and recommend it to everyone."

- SM-20-A  
customer review



SM-CAL1

## SM-CAL1 Sound Meter Calibrator

This instrument generates the fixed sound level signals needed to calibrate sound level meters.


- Two output levels: 94 dB and 114 dB
- Output frequency: 1000Hz
- Fits 0.5" microphones
- Easy one-handed operation
- Low battery indicator
- CE: conforms to ANSI S1.40 – 1984 and IEC942 – 1988 Class 2

**INCLUDED ACCESSORIES:** Battery (installed), user manual



# Solar Energy and Battery Testers

Amprobe solar solutions provide you with the tools to knowledgeably install, maintain, and troubleshoot solar systems as well as analyze the energy efficiency of solar panels, water heaters, and windows. Use Amprobe battery testers not only for green energy applications, but testing UPS and battery back-up systems.



## SOLAR-100 Power Meter

Optimize the placement of solar systems and analyze window efficiency with the SOLAR-100. Measure solar output and calculate overall energy and efficiency.

- Windows performance testing: calculate and verify heating or heat reduction caused by direct sunlight
- Research the location of solar panels or solar water heaters
- Measures solar power and transmission
- Power mode measures incident solar radiation
- Transmission mode calculates the percentage of solar power transmission through materials such as windows
- Convenient display with remote sensor technology
- Selectable measurement units (W/m<sup>2</sup> or BTU/ft<sup>2</sup>xh)
- Min/max function identifies locations with maximum or minimum power
- Also useful for physics and optical laboratories, meteorology, agriculture



Solar-100

| FEATURE     | SOLAR-100  |
|-------------|--|
| Solar Power | Up to 2000 W/m <sup>2</sup> , 634 BTU/(ft <sup>2</sup> xh) |
| Max/Min     | •  |
| Data Hold   | •  |

**INCLUDED ACCESSORIES:** Battery (installed), carrying case, user manual



### TOP RATED

*"A great instrument."*

*"This is an excellent device for quick measurements of irradiance out in the field. I was surprised that it can measure BTUs as well as headlight brightness and window tint."*

*It can also demonstrate the advantages of tracking and the effects of cloud cover. Great value for the money."*

- SOLAR-100 customer reviews

## SOLAR-600 Solar Analyzer

Install, maintain, troubleshoot and evaluate the efficiency of solar panels with this these professional analyzers. The SOLAR-600 also offers real-time data logging and PC downloads for further analysis.

- Determine the proper inverter size and optimum power output position of panels
- Identify broken or worn-out cells
- I-V curve test with cursor for solar cells
- Maximum solar power (Pmax) search by auto-scan
- Maximum voltage (Vmaxp) at Pmax
- Maximum current (Imaxp) at Pmax
- Voltage at open circuit (Vopen)
- Current at short circuit (Ishort)
- I-V curve with cursor
- Calculation of panel efficiency (%)
- Manual single point test
- Real time datalogging and PC download



SOLAR-600

| FEATURE               | SOLAR-600                                   |
|-----------------------|---|
| DC Voltage:           | 0.000 V → 9.999 V, 10.00 V → 60.00 V        |
| DC Current:           | 0.01A → 9.99 A, 10.0 A → 12.0 A             |
| DC Current Simulation | 0.01 A → 9.99 A, 10 A → 12 A                |
| Power                 | 0 W → 720 W                                 |
| Efficiency            | •   |
| Scan delay            | 0 mS → 3000 mS                              |
| Alarm                 | •   |
| Solar Panel Area      | 0.001 m <sup>2</sup> → 9999 m <sup>2</sup>  |
| Standard Light Source | 10 W/m <sup>2</sup> → 1000 W/m <sup>2</sup> |
| Data Storage Memory   | 99 records                                  |
| Data Logging          | •   |

**INCLUDED ACCESSORIES:** User manual, rechargeable battery pack (installed), AC adapter, USB cable and software CD, test leads, carrying case



### Recommended Accessories

**SOLAR-BAT1** Rechargeable Lithium Battery SOLAR-600 (Replacement accessory)



## BAT-250 Battery Tester

The Amprobe BAT-250 Battery Tester is designed for one-handed, comfortable and reliable battery measurements. The uniquely designed tester offers an ergonomic slider and a v-shaped side cradle to better hold batteries in place during testing. The contoured case shape fits neatly in your hand. Testing your batteries has never been easier.

- Quickly indicates if batteries are "good", "low" or "replace"
- Test standard and rechargeable batteries: 9V, AAA, AA, C, D, and 1.5 V button/coin/watch
- Ergonomically designed to contour to your hand for easy operation
- No batteries required to operate
- Large, upright display is easy to read
- V-shaped side cradle holds batteries securely in place during testing for consistently accurate results
- High-quality 9V contacts make tests simple and error-free
- Slider is shaped for one-handed testing

| BAT-250 Battery Tester   |  |
|--------------------------|--|
| I Max at F.S.D (typical) | 1.5 V: 375 mA, 9 V: 40 mA                              |
| Normal load (typical)    | 1.5 V: 4 Ω, 9 V: 215 Ω                                 |
| Dimensions (H x W x D)   | 4.3 x 2.9 x 1.1 in (110 x 74 x 29 mm)                  |
| Battery size             | 9 V, AAA, AA, C, D and 1.5 V button/coin/watch battery |
| Weight                   | Approximately 0.11 lb (50 g)                           |
| Certification            | CE   |

| Battery Type:                                     | Battery Indicator (typical): |       |         |
|---|------------------------------|-------|---------|
|   | REPLACE                      | LOW   | GOOD    |
| AAA, AA, C, D and 1.5 V button/coin/watch battery | < 0.9 V                      | 0.9 V | > 1.0 V |
| 9 V   | < 5.3 V                      | 5.3 V | > 6.5 V |

**INCLUDED ACCESSORIES:** User manual



BAT-250


Slider for testing AAA, AA, C, D, and 1.5 V button/coin/watch batteries.

Upright display is easy to read.



BAT-250

Side cradle holds standard battery sizes.



BAT-250

Tests 9V batteries

## BAT-500 Battery Tester

Here's the quick, accurate way to test back-up batteries and UPS systems without taking batteries off line.

- Comparator function to quickly access battery condition as Pass, Warning or Fail
- Store up to 99 user programmable settings for quick battery diagnostics
- Test battery impedance to calculate its true life
- Works with most batteries: compact storage batteries, alkaline and lead-acid up to 500 Ah
- Resistance measurement up to 40 ohms and voltage up to 40 V
- Simultaneously measure battery resistance and voltage
- Compact and lightweight
- For trending/life cycle analysis download test results to a PC

| FEATURE                  | BAT-500  |
|--------------------------|--|
| Maximum Battery Capacity | Up to 500 amp hours  |
| Battery Type             | Alkaline, Nickel-Metal Hydride (NiMH), Nickel-Cadmium (NiCd), Lithium-ion (Li-ion) and lead-acid batteries |
| DC Voltage               | 4.000 V, 40.00 V   |
| Impedance                | 40 mΩ, 400 mΩ, 4 Ω, 40 Ω   |
| Data Capture Memory      | 500 data sets  |
| Data Logging Memory      | 9600 data sets   |
| PC Download              | •  |

**INCLUDED ACCESSORIES:** User manual, software manual, batteries, AC adaptor, RS232C (to USB Bridge) cable, software CD, kelvin clips



BAT-500

## CR50A Capacitance Tester

Inspect and verify components for quality control by quickly checking circuits with this full-range capacitance and resistance meter.

- Dual zero adjustments pots to null strays and test leads
- Special "low ohms" range
- "Zero adjust" pots for low ohms and capacitance ranges
- Low battery indication



CR50A



LCR55A

## LCR55A Inductance, Capacitance and Resistance Tester

The ultimate electronic component verifier measures inductance, capacitance, resistance, transistors, diodes and microwave diodes.

- Plug-in test slots and test leads with threaded alligator clips for precision testing
- Data hold and max hold
- "Zero adjust" pot for ohms
- Low battery indication
- Auto power-off

| FEATURE         | CR50A   | LCR55A                                     |
|-----------------|---|--|
| Resistance      | 20 Ω, 200 Ω, 2 kΩ, 20 kΩ, 200 kΩ, 2 MΩ, 20 MΩ     | 20 Ω, 200 Ω, 2 kΩ, 20 kΩ, 2 MΩ, 20 MΩ      |
| Capacitance     | 200 pF, 2000 pF, 2 μF, 20 μF, 200 μF, 2 mF, 20 mF | 200 pF, 2000 pF, 2 μF, 20 μF, 200 μF, 2 mF |
| Inductance      | -   | 200 μH, 2 mH, 200 mH, 200 H                |
| Transistors     | -   | Hfe, I <sub>ceo</sub> (NPN, PNP)           |
| Diodes          | •   | Standard (3 V) & microwave oven (8 V)      |
| Continuity Test | •   | •  |

**INCLUDED ACCESSORIES:** User manual, test leads with alligator clips, battery (installed)



★★★★★  
**TOP RATED**

*"Very reliable."*

*"We work in the HVAC industry and capacitors are a common issue. The Amprobe LCR55A Capacitance Tester has been a great investment and time saver. A quick check and record has identified weak capacitors and saved us from costly call backs."*

- LCR55A customer reviews

## R-115S Remcon Momentary Switch Relay (3-wire)

## RC-120S Remcon Closet Light Relay (2-wire)

When you need low-voltage control circuits for safe operation in industrial and process control environments, choose these low-voltage relays with built-in transformers. Each unit operates independently, so you can install one relay and operate it with as many switches as needed or control multiple relays with a single switch.

- Uses light 22 gauge wire, saving the time and expense of pulling Romex or armored cable
- Simplifies wiring – no need to wire back to separate low voltage transformers
- Operates silently so you can install relays at the fixture instead of at a remote location

| FEATURE                         | R-115S                                       | RC-120S |
|---------------------------------|--|---------|
| AC Voltage                      | 105 V → 125 V                                |         |
| AC Current                      | Up to 6.5 A (1/4 HP max motor load at 120 V) |         |
| Frequency                       | 60 Hz  |         |
| Safe Control Switching, Maximum | 10 V DC 10 milliamps                         |         |



R-115S



RC-120S



# Accessories

Get the most out of your Amprobe tools with a wide range of carrying cases, probes, current transducers, test leads, software and more. Visit [www.Amprobe.com](http://www.Amprobe.com) to view the full line of accessories and determine which ones are available for your Amprobe test tools.



# Accessories

## Test Leads



DL243D

**DL243D**

48" long silicone lead wires, probe tips, alligator clips, spade lugs, fold-out carrying case



DL248D

**DL248D**

Same as DL243D plus spring loaded crimp tips and red tip length extender



TL35B

**TL35B**

Standard leads: 40" PVC insulated lead with standard tips plus threaded large alligator clips, CE approved alligator clips, 0.6" jaw, shrouded 90° banana plugs, one red and one black leads and clips



TL1500

**TL1500**

Heavy duty test leads  
CAT IV / 1000 V, 1500 V MAX



HS-1

## HS-1 Hanging Strap

The HS-1 Hanging Strap is a three-way hanger for the AT-7000-T Transmitter or any Amprobe digital multimeter. It allows convenient hanging of the unit, placement on a belt or as a stand.



ELS2A

## Line Splitter

**ELS2A, AC Line Splitter**

- Measures load current without splitting line cord
- Two measurement points, X1 and X10 for increased sensitivity
- Built-in voltage measurement jacks
- 115 V, 15 A



CT235A

## Current Clamps

**CT235A** AC/DC current clamp, 1000 A (50/10 kHz), mV output, 1.2" max conductor


**CT237B** AC/DC current clamp, 200 A (50/10 kHz), mV output, .75" max conductor

**CT238A** AC/DC current clamp, 20 A (50/20 kHz) Low current version



CT237A

CT238A



TPK-59

## Thermocouple

**TPK-59, Thermocouple**

- Accessory for multimeters and clamp-ons with temperature input
- Measures temperature from -50°F ~ 600°F
- Plugs directly to a meter without additional adapters



# Carrying Case Directory

|                  | CC-ACDC | DC205C | CC-MEG | SV-U | VC221B | VC3A | VC30A | CC-DM-III | CC-300 PRO | CC-7000 |
|------------------|---------|--------|--------|------|--------|------|-------|-----------|------------|---------|
| 30XR-A           |         |        |        |      | •      |      |       |           |            |         |
| 33XR-A           |         |        |        |      | •      |      |       |           |            |         |
| 34XR-A           |         |        |        |      | •      |      |       |           |            |         |
| 37XR-A           |         |        |        |      | •      |      |       |           |            |         |
| 38XR-A           |         |        |        |      | •      |      |       |           |            |         |
| 5XP-A            |         |        |        |      | •      |      |       |           |            |         |
| 15XP-B           |         |        |        |      | •      |      |       |           |            |         |
| 35XP-A           |         |        |        |      | •      |      |       |           |            |         |
| AC40C            |         |        |        |      |        |      | •     |           |            |         |
| AC50A            |         |        |        |      |        |      | •     |           |            |         |
| AC68C            | •       |        |        |      |        |      |       |           |            |         |
| AC75B            | •       |        |        |      |        |      |       |           |            |         |
| ACD-50NAV        | •       |        |        |      |        |      |       |           |            |         |
| ACD-51NAV        | •       |        |        |      |        |      |       |           |            |         |
| ACDC-52NAV       | •       |        |        |      |        |      |       |           |            |         |
| ACD-53NAV        | •       |        |        |      |        |      |       |           |            |         |
| ACDC-54NAV       | •       |        |        |      |        |      |       |           |            |         |
| ACD-205W         | •       |        |        |      |        |      |       |           |            |         |
| ACD-215W         | •       |        |        |      |        |      |       |           |            |         |
| ACD-225W         | •       |        |        |      |        |      |       |           |            |         |
| ACD-235W         | •       |        |        |      |        |      |       |           |            |         |
| ACD-10 PLUS      |         |        |        | •    |        |      |       |           |            |         |
| ACD-10 TRMS-PLUS |         |        |        | •    |        |      |       |           |            |         |
| ACD-14 PLUS      |         |        |        | •    |        |      |       |           |            |         |
| ACD-14 TRMS-PLUS |         |        |        | •    |        |      |       |           |            |         |
| ACD-15 TRMS-PRO  | •       |        |        |      |        |      |       |           |            |         |
| ACD-16 TRMS-PRO  | •       |        |        |      |        |      |       |           |            |         |
| ACD-41PQ         | •       |        |        |      |        |      |       |           |            |         |
| ACD-45PQ         |         |        |        | •    |        |      |       |           |            |         |
| ACD-6 PRO        | •       |        |        |      |        |      |       |           |            |         |
| ACDC-100         | •       |        |        |      |        |      |       |           |            |         |
| ACDC-100 TRMS    | •       |        |        |      |        |      |       |           |            |         |
| ACD-3300 IND     | •       |        |        |      |        |      |       |           |            |         |
| ACDC-3400 IND    | •       |        |        |      |        |      |       |           |            |         |
| ACDC-400         |         |        |        | •    |        |      |       |           |            |         |
| AD40B            |         |        |        |      |        |      | •     |           |            |         |
| AM-140-A         |         |        |        |      | •      |      |       |           |            |         |
| AM-160-A         |         |        |        |      | •      |      |       |           |            |         |
| AM-220           |         |        |        |      | •      |      |       |           |            |         |
| AM-240           |         |        |        |      | •      |      |       |           |            |         |
| AM-250           |         |        |        |      | •      |      |       |           |            |         |
| AM-270           |         |        |        |      | •      |      |       |           |            |         |
| AM-500           |         |        |        |      |        |      | •     |           |            |         |
| AM-510           |         |        |        |      | •      |      |       |           |            |         |
| AM-520           |         |        |        |      | •      |      |       |           |            |         |
| AM-530           |         |        |        |      | •      |      |       |           |            |         |
| AM-560           |         |        |        |      | •      |      |       |           |            |         |
| AM-570           |         |        |        |      | •      |      |       |           |            |         |
| AM8C             |         |        |        |      | •      |      |       |           |            |         |
| CR50A            |         |        |        |      |        |      | •     |           |            |         |
| DGC-1000A        | •       |        |        |      |        |      |       |           |            |         |
| DM73C            |         |        |        | •    |        |      |       |           |            |         |
| DM78C            |         |        |        |      |        |      | •     |           |            |         |
| DM7C             |         |        |        |      | •      |      |       |           |            |         |
| DM9C             |         |        |        |      | •      |      |       |           |            |         |
| HD110C           |         | •      |        |      | •      |      |       |           |            |         |
| HD160C           |         | •      |        |      | •      |      |       |           |            |         |
| INSP-3           |         |        |        |      | •      |      |       |           |            |         |
| LCR55A           |         |        |        |      | •      |      |       |           |            |         |
| LH41A            |         |        |        | •    |        |      |       |           |            |         |
| PM51A            |         |        |        |      |        | •    |       |           |            |         |
| PM55A            |         |        |        |      |        | •    |       |           |            |         |
| RS-1007          | •       |        |        |      |        |      |       |           |            |         |
| RS-3 PRO         | •       |        |        |      |        |      |       |           |            |         |
| TIC 300 PRO      |         |        |        |      |        |      |       |           | •          |         |
| GP-2A            |         |        | •      |      |        |      |       |           |            |         |
| DM III Multitest |         |        |        |      |        |      |       | •         |            |         |
| AMB-45           |         |        | •      |      |        |      |       |           |            |         |
| AT-7020 / 7030   |         |        |        |      |        |      |       |           |            | •       |




**CC-ACDC**  
Soft Pouch Zippered Carrying Case  
11.5 x 4.5 x 2.8"  
(292 x 114 x 70 mm)



**DC205C**  
Deluxe Heavy Duty Carrying Case  
9.6 x 4.7 x 4.3"  
(244 x 119 x 109 mm)



**CC-MEG**  
Soft Carrying Case  
10 x 8.5 x 3.25"  
(254 x 216 x 89 mm)



**SV-U**  
Soft Pouch Zippered Carrying Case  
8.5 x 3.0 x 2.5"  
(216 x 76 x 64 mm)



**VC221B**  
Padded Vinyl Carrying Case  
8.5 x 4.5 x 2.5"  
(216 x 114 x 64 mm)



**VC3A**  
Rugged zippered Carrying Case  
4.5 x 2.2 x .4"  
(114 x 56 x 10mm)



**VC30A**  
Vinyl Carrying Case  
7.5 x 3.4 x 1.5"  
(191 x 86 x 38 mm)



**CC-DM-III**  
Deluxe Heavy Duty Carrying Case  
18.3 x 15.0 x 7.3"  
(465 x 381 x 184 mm)



**CC-300 PRO**  
Leather Carrying Case  
10.84 x 4.20 x 2.40"  
(275 x 107 x 70 mm)



**CC-7000**  
Custom Hard Carrying Case  
16 x 13 x 7 in  
(40.6 x 33 x 17.8 cm)

## Product Fuse Directory

| MODEL                         | PART NUMBER   | FUSE TYPE              |
|-------------------------------|---------------|------------------------|
| RS-1007                       | FP500         | 0.5A/1000V, 6.3X32mm   |
| RS-3 PRO                      | FP500         | 0.5A/1000V, 6.3X32mm   |
| AM-250                        | FP650         | 630mA/500V, 6X32mm     |
|                               | FA-12.5A/500V | 12.5A/500V, 6X32mm     |
| AM-270                        | FP160         | 10A/600V, 10X38mm      |
|                               | FUSE-1A       | 1A/600V, 10X38mm       |
| AM-500                        | FA-0.5A/700V  | 0.5A/700V, 6.3X32mm    |
|                               | FP400         | 10A/600V, 6.3X25 mm    |
| AM-510                        | FP500         | 0.5A/1000V, 6.3X32mm   |
|                               | FP400         | 10A/600V, 6.3X25 mm    |
| AM-520                        | FP500         | 0.5A/1000V, 6.3X32mm   |
|                               | FP410         | 11A/1000V, 10X38mm     |
| AM-530                        | FP500         | 0.5A/1000V, 6.3X32mm   |
|                               | FP410         | 11A/1000V, 10X38mm     |
| AM-560                        | FP500         | 0.5A/1000V, 6.3X32mm   |
|                               | FP410         | 11A/1000V, 10X38mm     |
| AM-570                        | FP500         | 0.5A/1000V, 6.3X32mm   |
|                               | FP410         | 11A/1000V, 10X38mm     |
| AM-140-A                      | FP160         | 10A/600V, 10X38mm      |
|                               | FUSE-1A       | 1A/600V, 10X38mm       |
| AM-160-A                      | FP412         | 0.44A/1000V, 10X38mm   |
|                               | FP410         | 11A/1000V, 10X38mm     |
| AM-220                        | 5X20-250.5    | 0.5A/250V, 5X20mm      |
|                               | 6X32-250V10A  | 10A/250V, 6X32mm       |
| AM-240                        | 5X20-250.5    | 0.5A/250V, 5X20mm      |
|                               | 6X32-250V10A  | 10A/250V, 6X32mm       |
| 30XR-A                        | FP160         | 10A/600V, 10X38mm      |
|                               | FP375         | 0.25A/700V, 6.3X32mm   |
| 33XR-A                        | FP100         | 10A/1000V, 10X3 8mm    |
|                               | FP300         | 0.315A/1000V, 6.3X32mm |
| 34XR-A                        | FP100         | 10A/1000V, 10X38mm     |
|                               | FP300         | 0.315A/1000V, 6.3X32mm |
| 37XR-A                        | FP100         | 10A/1000V, 10X38mm     |
|                               | FP500         | 0.5A/1000V, 6.3X32mm   |
| 38XR-A                        | FP100         | 10A/1000V, 10X38mm     |
|                               | FP500         | 0.5A/1000V, 6.3X32mm   |
| 5XP-A                         | FP300         | 0.315A/1000V, 6.3X32mm |
| 15XP-B                        | FP200         | 2A/1000V, 6.3X32mm     |
| 35XP-A                        | FP200         | 2A/1000V, 6.3X32mm     |
| HD110C                        | FP700         | 2A/1500V, 8X65mm       |
| HD160C                        | FP700         | 2A/1500V, 8X65mm       |
| DM7C                          | FP900         | 200mA / 700V, 6.3X32mm |
| DM9C                          | FA-6X32/.63   | 0.63A/500V, 6X32mm     |
|                               | FP540         | 10A/600V, 6.3X32 mm    |
| PRM-4                         | FP900         | 200mA/700V, 6.3X32mm   |
| AMB-45                        | FA-0.5A/700V  | 0.5A/700V, 6.3X32mm    |
| S2600                         | 380.25-6X32   | 0.25A/380V, 6X32mm     |
| T-100,T-300<br>(CT-100, 326B) | 3AG-312.250   | 0.25A/250V, 6.3X32mm   |
| T2200 (AT-200X)               | 2502-6X32     | 2A/250V, 6X32mm        |
| T-4000 (AT-400X)              | FA6X46MM      | 0.25A/1000V, 6X46mm    |
| X1000 (AT1000)                | 380.25-6X32   | 0.25A/380V, 6X32mm     |
| CR50A                         | FP125         | 0.1A/250V, 5X20mm      |
| LCR55A                        | FP125         | 0.1A/250V, 5X20mm      |
| AU92                          | FP520         | 0.5V/500V, 6.3X32 mm   |
|                               | FP540         | 10A/600V, 6.3X32 mm    |

## Software and Cables

Transfer measurement data to your computer with these kits.

For complete details on Amprobe software and to download the latest versions, please visit [www.amprobe.com/softwaredownloads.html](http://www.amprobe.com/softwaredownloads.html)

## Download Suite Software

Download Suite is a free software package compatible with most of the Amprobe instruments with download capabilities. Enjoy the benefits of this powerful software package for a wide selection of Amprobe megohmmeters, ground resistance testers, multimeters, and power quality recorders.

- Install software once and use it with all supported Amprobe products
- All instruments share the same file format. You can open files recorded by you, other people, or the Amprobe instruments right on your PC.
- Download Suite automatically checks your version for upgrades and keeps your version current.
- Windows7 compatible

## USB-KIT2

- Download software with connection cable for Amprobe clamp meters

## USB-KIT3

- Download software with connection cable for Amprobe multimeters

## RS-USB, USB to RS-232 Adapter

- Converts the USB port of a PC to RS-232
- Supports Windows 95 (OSR2X), 98, 2000, ME, XP, Vista, Mac 8.6 and higher
- Works with Amprobe instruments with download capabilities
- Works with many other products with USB ports, including cameras, Palm Pilot, card readers, mouse, security systems, etc.
- Frees up the serial port for other uses

## TM-SWA, USB Cable and Software

- Allows for real-time data downloads from TMA10A and TMD90A
- Records two channels simultaneously



USB-KIT2



USB-KIT3



TM-SWA

# Amprobe Product Index

| MODEL #          | PRODUCT # | PG # |
|------------------|-----------|------|
| 15XP-B           | 3534088   | *    |
| 30XR-A           | 2727774   | *    |
| 33XR-A           | 2727788   | *    |
| 34XR-A           | 2727795   | *    |
| 35XP-A           | 2727849   | *    |
| 37XR-A           | 2727808   | 14   |
| 38XR-A           | 2727824   | 14   |
| 5XP-A            | 2727851   | *    |
| AC50A            | 3033017   | 10   |
| AC68C            | 2727919   | *    |
| AC75B            | 2727885   | *    |
| ACD-10 PLUS      | 3037808   | 8    |
| ACD-10 TRMS-PLUS | 3037813   | *    |
| ACD-14 PLUS      | 3086905   | 8    |
| ACD-14-PRO       | 4718977   | 9    |
| ACD-14 TRMS-PLUS | 3086910   | *    |
| ACD-15 TRMS-PRO  | 2730690   | *    |
| ACD-16 TRMS-PRO  | 2730713   | *    |
| ACD-20SW         | 3472723   | 8    |
| ACD-21SW         | 3472738   | *    |
| ACD-22SW         | 3804934   | *    |
| ACD-23SW         | 3804934   | 8    |
| ACD-3300 IND     | 3434877   | *    |
| ACD-41PQ         | 2730760   | *    |
| ACD-45PQ         | 3730013   | *    |
| ACD-50NAV        | 3729945   | 6    |
| ACD-51NAV        | 3729950   | 6    |
| ACD-53NAV        | 3729977   | *    |
| ACD-6 PRO        | 2730785   | 10   |
| ACDC-100         | 2740452   | *    |
| ACDC-100 TRMS    | 2740465   | *    |
| ACDC-3400 IND    | 3434889   | 9    |
| ACDC-400         | 2730810   | *    |
| ACDC-52NAV       | 3729961   | 6    |
| ACDC-54NAV       | 3729989   | 6    |
| ACF-3000DM-A     | 2732395   | *    |
| AM-140-A         | 3730024   | *    |
| AM-160-A         | 3730036   | *    |
| AM-250           | 3524986   | *    |
| AM-270           | 3524999   | *    |
| AM-500           | 4018624   | 16   |
| AM-510           | 4018636   | 13   |
| AM-520           | 4018649   | *    |
| AM-530           | 4018651   | 13   |
| AM-560           | 4210333   | *    |
| AM-570           | 4210340   | 13   |
| AMB-110          | 3730335   | 33   |
| AMB-2            | 2730984   | *    |
| AMB-25           | 2730991   | 32   |
| AMB-3            | 2731008   | 34   |
| AMB-45           | 2731024   | 32   |
| AMB-50           | 3730288   | 33   |
| AMB-55           | 3730320   | 33   |
| AMC-2            | 2731060   | 34   |
| AMC-3            | 2731072   | 34   |
| AMC-4            | 2731085   | 34   |
| AMP-25           | 4588254   | 7    |
| AMP-210          | 4560537   | 5    |
| AMP-220          | 4560543   | 5    |
| AMP-310          | 4560555   | 5    |
| AMP-320          | 4560562   | 5    |
| AMP-330          | 4560570   | 5    |

| MODEL #   | PRODUCT # | PG #  |
|-----------|-----------|-------|
| AT-1000   | 2731097   | 28    |
| AT-2004-A | 4416090   | 28    |
| AT-2005-A | 4416104   | 28    |
| AT-3500   | 3435058   | 26    |
| AT-4001-A | 4416052   | 27    |
| AT-4003-A | 4416065   | *     |
| AT-4004-A | 4416076   | 27    |
| AT-4005-A | 4416083   | 27    |
| AT-7020   | 4313854   | 24    |
| AT-7030   | 4313868   | 24    |
| BAT-200   | 3473003   | *     |
| BAT-250   | 3473003   | 53    |
| BAT-500   | 3474946   | 53    |
| BT-120    | 3472789   | *     |
| BT-250    | 2731177   | 29    |
| CM100     | 3311826   | 48    |
| CO2-100   | 3475094   | 48    |
| CO2-200   | 3475100   | 48    |
| CR50A     | 3026965   | 54    |
| CT-100    | 2731189   | 29    |
| CT-326-C  | 4416119   | 29    |
| CT235A    | 3026809   | 56    |
| CT237B    | 3511514   | 56    |
| CT238A    | 3026827   | 56    |
| DGC-1000A | 2731217   | 35    |
| DL243D    | 3026853   | 56    |
| DL248D    | 3026866   | 56    |
| DM-5      | 4724171   | 33    |
| DM73C     | 2727739   | 16    |
| DM78C     | 3156830   | *     |
| ECB50A    | 3016966   | *     |
| ELS2A     | 3027072   | 10/56 |
| GP-2A     | 4129187   | 35    |
| GSD600    | 3311832   | 47    |
| HD110C    | 2670779   | 15    |
| HD160C    | 2670787   | 15    |
| HS-1      | 4544565   | 56    |
| INSP-3    | 3503207   | 18    |
| IR-450    | 4227490   | 39    |
| IR608A    | 3015690   | 39    |
| IR-708    | 0000000   | 38    |
| IR-710    | 4109553   | 38    |
| IR-712    | 4109566   | *     |
| IR-720    | 4109575   | 38    |
| IR-730    | 4109582   | 38    |
| IR-750    | 4109594   | 38    |
| LAN-1     | 3052401   | 22    |
| LCR55A    | 3026976   | 54    |
| LH41A     | 3030898   | 10    |
| LM-100    | 3052348   | 49    |
| LM-120    | 3052353   | 49    |
| LM-200LED | 3730217   | 49    |
| LT-10     | 4222120   | 18    |
| MAN15     | 3474993   | *     |
| MAN30     | 3475009   | *     |
| MANO2-A   | 3477279   | *     |
| MO-100    | 3474954   | 20    |
| MT-10     | 3503178   | 44    |
| MTL-90B   | 2733170   | *     |
| PK-110    | 0000000   | 22    |
| PM51A     | 2727700   | 16    |
| PM55A     | 2727721   | 16    |

| MODEL #     | PRODUCT # | PG # |
|-------------|-----------|------|
| PRM-4       | 3239635   | *    |
| PRM-6       | 4375950   | 20   |
| PY-1A       | 3503229   | 22   |
| R-115S      | 2734454   | 54   |
| RC-120S     | 2731504   | 54   |
| RLD-1       | 3474968   | 46   |
| RS-1007 PRO | 3467476   | 9    |
| RS-3 PRO    | 3467465   | *    |
| SM-10       | 3052366   | 50   |
| SM-20-A     | 3477333   | 50   |
| SM-CAL1     | 3052382   | 50   |
| SOLAR-100   | 3474979   | 52   |
| SOLAR-600   | 3730242   | 52   |
| ST-101B     | 3016975   | 21   |
| ST-102B     | 4160817   | 21   |
| TACH-10     | 3730008   | 49   |
| TACH20      | 3311961   | 49   |
| TH-1        | 3311871   | 40   |
| TH-3        | 3027060   | 40   |
| THWD-3      | 3033042   | 40   |
| THWD-5      | 3311803   | 40   |
| TIC 300 PRO | 3467441   | 19   |
| TIC 410A    | 3107749   | 19   |
| TL1500      | 2696277   | 56   |
| TL245A      | 3068215   | *    |
| TL35B       | 3068232   | 56   |
| TL36A       | 3034444   | *    |
| TMA-21HW    | 3730239   | 46   |
| TMA10A      | 2817785   | 45   |
| TMA40-A     | 3477287   | 45   |
| TMA5        | 3503169   | 44   |
| TMD-50      | 3730150   | *    |
| TMD-53      | 3730085   | *    |
| TMD-56      | 3730138   | 41   |
| TMD-10      | 3052394   | *    |
| TMD90A      | 2817797   | *    |
| TMULD-300   | 2731543   | 47   |
| TPK-59      | 2733660   | 56   |
| TR200-A     | 3477302   | 42   |
| TR300       | 3311844   | 42   |
| TX900       | 3390352   | *    |
| ULD-300     | 2734431   | 47   |
| VP-1000SB   | 4160821   | 21   |
| VP-440      | 2734332   | 21   |

\*This product is available for order but not in the catalog. For detailed specifications go to [www.Amprobe.com](http://www.Amprobe.com)

## Where to Buy

Visit [www.amprobe.com/wheretobuy](http://www.amprobe.com/wheretobuy) to find authorized Amprobe dealers in your area.

## New Products

### ACD-14-PRO Dual Display TRMS Clamp Multimeter

The ACD-14-PRO offers a complete range of measuring functions for both HVAC and electrical applications, and features a large backlit LCD dual display that simultaneously displays voltage and amps.

See Pg. 9 for more information.

### AT-7000 Advanced Wire Tracer

Get accurate results in minutes with new features and technologies that simplify wire tracing and breaker identification. The Receiver's patented Smart Sensor™, with its innovative new antenna design and advanced signal processor, clearly displays the location and orientation of energized wires in walls, floors and ceilings on the large color TFT LCD screen.

See Pg. 24 for more information.

### AMP-200/AMP-300 Series

The Amprobe AMP-200 and -300 Series True-RMS Clamp Meters offer a complete range of measurement functions for modern electrical environments, motor testing and HVAC applications. All models feature True-RMS sensing, low pass filters and fast response processors for quick, error-free measurements.

See Pg. 5 for more information.

### AMP-25 AC/DC TRMS Mini-Clamp

Small size doesn't mean small features. The Amprobe AMP-25 Mini-Clamp is pocket-sized, enabling quick and easy spot checks of electrical systems. With its rugged construction and CAT III 600V rating, the AMP-25 is a must-have professional troubleshooting tool for commercial electricians and electrical contractors.

See Pg. 7 for more information.

### PRM-6 Phase Sequence and Motor Rotation Tester

The PRM-6 Phase Sequence and Motor Rotation Tester can test the motor rotation of 3-phase systems and verify 3-phase receptacle wiring and phase sequencing with test leads. It also features wireless motor rotation detection that senses motor rotation direction without use of test leads.

See Pg. 20 for more information.

## 2016 Product Catalog



# Hard at Work Since 1948

#### www.Amprobe.com

Visit our web site for full data sheets, application notes, software downloads, special promotions and more.

#### Amprobe®

www.Amprobe.com  
info@amprobe.com  
Everett, WA 98203  
tel: 877-AMPROBE (267-7623)

#### Amprobe® Europe

www.beha-amprobe.com  
info@amprobe.de  
In den Engematten 14  
79268 Glottental, Germany  
tel: +49 (0) 7684 8009 - 0

#### © 2016 Amprobe Test Tools

All rights reserved.  
Printed in the U.S.A.  
2765603\_L

Specifications subject to change without notice.