



STEEL & CONCRETE CONSTRUCTION



TABLE OF CONTENTS

1	PLIERS
3	WORK @ HEIGHT TOOLS
4	BOLT & ELECTRODE BAGS
5	TOOL BELTS
6	STRUCTURAL IRON WORKER
11	CONCRETE CONSTRUCTION
14	TOOL POUCHES
16	CABLE/BOLT CUTTERS
19	JOURNEYMAN™ SHEET METAL SNIPS
20	KNIVES
22	HOLEMAKING
24	HAMMERS
25	SAFETY
27	GLOVES
28	JOURNEYMAN™ GLOVES

WARNING SYMBOLS



Safety alert symbol: Indicates a hazard.



NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.




Always ensure that you and the persons in the vicinity wear approved eye protection.



It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.

PLIERS



"Handform" handles for full gripping and cutting power.

Plastic-dipped handles for comfort and ease of identification.

Unique handle tempering helps absorb the "snap" when cutting wire.

Precision-hardened plier head for on-the-job toughness.

Hot-riveted joint ensures smooth action and no handle wobble.

Induction hardened cutting knives for long life.

FORGED STEEL

from Klein's US-made, proprietary blend

2000 SERIES Cuts ACSR, screws, nails, and most hardened wire.



Ironworker's Pliers

Use to twist and snip soft annealed rebar tire wire. The knurled jaws also aid in easy twisting and turning. These pliers feature a hook-bend in the handle for added grip and leverage. Unique handle tempering helps absorb the "snap" when cutting wire. Split ring for tethering available on "TT" Series.

Cat. No.	Overall Length	Nose Type	Handle Finish	Handle Color
Side-Cutting				
201-7CST	9-1/8" (232 mm)	Square	plain	N/A
D201-7CST	9-1/4" (235 mm)	Square	plastic-dipped	dark blue
D201-7CSTT	9-1/4" (235 mm)	Square	plastic-dipped	dark blue
213-9ST	9-1/4" (235 mm)	New England	plain	N/A
D213-9ST	9-3/8" (238 mm)	New England	plastic-dipped	dark blue
D213-9STT	9-3/8" (238 mm)	New England	plastic-dipped	dark blue
D2000-7CST*	9-1/4" (235 mm)	Square	plastic-dipped	royal blue
D2000-9ST*	9-3/8" (238 mm)	Square	plastic-dipped	royal blue
Diagonal-Cutting				
D248-9ST	9-3/16" (233 mm)	Tapered	plastic-dipped	red
D248-9STT	9-3/16" (233 mm)	Tapered	plastic-dipped	red

*Cuts ACSR, screws, nails, and most hardened wire.





MADE IN USA



D2000-9NE



D2000-49

Angled head to get into tight spaces



D228-8TT

Split ring for tethering



High-Leverage Pliers

Available in side or diagonal-cutting models, these pliers feature a high-leverage design. The rivet is closer to the cutting edge for greater cutting and gripping power than other plier designs. The 2000 Series have heavy-duty cutting knives for ACSR, screws, nails and most hardened wire. The angled head on the diagonal cutters easily gets into tight spaces. The “TT” series feature a split ring for tethering the pliers when working at height.

Cat. No.	Overall Length	Nose Type	Handle Finish	Handle Color
Side-Cutting				
D213-9NE	9-3/8" (238 mm)	New England	plastic-dipped	dark blue
D213-9NETT	9-3/8" (238 mm)	New England	plastic-dipped	dark blue
D2000-9NE*	9-3/8" (238 mm)	New England	plastic-dipped	royal blue
Diagonal-Cutting				
D248-8	8-1/16" (205 mm)	Tapered	plastic-dipped	red
D228-8	8-1/16" (205 mm)	Tapered	plastic-dipped	red
D228-8TT	8-1/16" (205 mm)	Tapered	plastic-dipped	red
D2000-48*	8-1/16" (205 mm)	Tapered	plastic-dipped	royal blue
D2000-49*	9" (228 mm)	Tapered	plastic-dipped	royal blue

*Cuts ACSR, screws, nails, and most hardened wire.





Why is it important?

In private industry, falling objects accounted for 10% of worker fatalities in 2013 and are the third leading cause of disabling workplace injuries. In 2012, falling objects caused 18% of contractor deaths, a 7% increase from 2011.

OSHA ranks being "struck by objects" as the third leading cause of disabling workplace injuries.

Klein Tools' growing line of tethers and tools for Work@Height are designed to protect workers on the job site as well as their tools.

- Keep your tools close at hand while working at height
- Allow for easy tool recovery in case of accidental drops
- Triple-locking carabiner for additional safety



Cat. No.	Max. Load Capacity	Relaxed Length	Stretched Length
TT1	10 lbs (4.5 kg)	32" (813 mm)	60" (1.5 m)
TT2	15 lbs (4.5 kg)	32" (813 mm)	51" (1.3 m)



Always use choke hitch formation



Attach tether through tether hole when available



Always use a load bearing anchor or attachment point

Heavy-Duty Torpedo Level with Tether Ring

- Powerful rare-earth magnets, 10x stronger than strip magnets, hold firmly to iron and steel surfaces



931-9RETT

- Three acrylic vials – plumb, level and 45° provide the necessary jobsite measurements
- Top read level window simplifies viewing in tight areas

Cat. No.	Overall Length
931-9RETT	9" (229 mm)

- ⚠ WARNINGS:**
- Inspect for wear before each use.
 - Do not use for human support.
 - Never connect over 5 lbs. (2.3 kg) to a person.
 - Do not use around moving or rotating equipment.
 - Tethers extend to anywhere from 3.5' to 5' (1.3 m to 1.5 m). Rig to avoid contact with objects below.
 - Always ensure cinch remains snug while in use.
 - Always attach carabiner end to anchor point.
 - Do not attach tether back onto itself.
 - Do not tie knots in tether.





PROUDLY BUILT IN USA

 WITH GLOBAL COMPONENTS

Leather Bolt Bag

- Split-leather construction.
- Bolt bag with bull-pin loop on each side.
- Tunnel loop fits belts up to 3" wide.



42247

Cat. No.	Length	Width	Depth
42247	5" (127 mm)	8-1/2" (216 mm)	8-1/2" (216 mm)

Bull-Pin and Bolt Bags

- Bull pin loops on each side for easy access
- Double bottom provides additional strength
- Cat. No. 5416OCTO has two D-rings on the front of the pouch and four on the inside for plenty of space to connect tethers.
- Cat. No. 5416TC and 5416TCP have drawstring closure on top



5416OCTO

Cat. No.	Belt Capacity	Belt Connection	Length	Width	Depth
5416OCTO	up to 3" (76 mm) wide	loop	5" (127 mm)	9" (229 mm)	9" (229 mm)
5416TC	up to 3" (76 mm) wide	tunnel	5" (127 mm)	9" (229 mm)	10" (254 mm)
5416TCP	up to 3" (76 mm) wide	tunnel	5" (127 mm)	9" (229 mm)	12" (305 mm)

VELCRO® is a registered trademark of Velcro Industries B.V.

Bull-Pin and Bolt Bags

- No. 4 flame-resistant canvas meets the performance requirement of NFPA -701.
- Bolt bag with bull-pin loop on each side.
- Double bottom for added durability.
- Tunnel loop fits belts up to 3" wide.
- For added protection when welding and grinding.



5416TFR

FR

Cat. No.	Height	Width	Depth
5416TFR	5" (127 mm)	9" (229 mm)	10" (254 mm)

Canvas Electrode Bag

- No. 4 flame-resistant canvas meets the performance requirement of NFPA -701.
- Heat-resistant, hard leather bottom.
- Web loop for sliding over belt.
- For added protection when welding and grinding.



5471FR

FR



Cat. No.	Diameter	Front Depth	Back Depth
5471FR	2-1/2" (64 mm)	12" (305 mm)	15-1/2" (394 mm)

Tool Belt with Quick-Release Buckle

- NOT an occupational protective belt. ONLY use as a tool belt.
- Forged, quick-release buckle for emergency situations where the user has to quickly disengage the belt (for example, when working over water or in grain elevators).
- Must be worn over the user's harness and clothing so it will drop free when released.
- Mildew-resistant cotton/polyester webbing for comfort and strength.

Designed for Quick Release

1. Pull free end of release strap to disengage other end from retainer.
2. Pulling action rotates clasp to open position.
3. Disengaged clasp allows belt to separate.



5425M

Cat. No.	Size
5425M	30" - 44" (762 mm - 1118 mm)
5425XL	38" - 58" (965 mm - 1473 mm)



5420L



5415

Heavy-Duty Tie-Wire Belts

- Strong double-tongue buckle with keeper.
- Has separate reel-strap with its own buckle that lets you quickly and conveniently put on or take off a Klein tie-wire reel and optional pad without removing the belt or your tool pouch.
- Leather construction.
- Belts listed are 2"(51 mm) wide.

Cat. No.	Waist Size	Belt Size Range
5420S	36" (914 mm)	32" - 40" (813 mm - 1016 mm)
5420	40" (1016 mm)	36" - 44" (914 mm - 1118 mm)
5420L	44" (1118 mm)	40" - 48" (1016 mm - 1219 mm)
5420XL	48" (1219 mm)	44" - 52" (1118 mm - 1321 mm)

Heavy-Duty Embossed Tool Belts

- Strong, heavy-duty leather.
- Equipped with a double-tongue buckle.
- Belts listed are 2" (51 mm) wide.

Cat. No.	Size
5415S	32" - 40" (813 mm - 1016 mm)
5415	36" - 44" (914 mm - 1118 mm)
5415L	40" - 48" (1016 mm - 1219 mm)
5415XL	44" - 52" (1118 mm - 1321 mm)



5245

Padded Tool Belts

- 2" (51 mm) wide tool belt and padded liner with breathable mesh interior.
- Thick, rugged leather ends.
- Side handles for ease of lifting.
- Metal connection points to attach suspenders for added support.

Cat. No.	Size
5245	31" - 34" (787 mm - 864 mm)
5246	35" - 39" (889 mm - 991 mm)
5247	40" - 44" (1016 mm - 1118 mm)

Leather Cushion Belt Pads

- Deluxe leather pad is 4" (102 mm) wide.
- Thick leather back with four snap-open straps for easy attachment to any belt up to 2" (51 mm) wide.
- Sponge-padded leather liner has rounded edges, and is permanently stitched to the back.
- Durable and comfortable pad to wear for prolonged work periods.
- When sizing a belt to accommodate this pad, add 2" (51 mm) to 4" (102 mm) to the belt waist size.



87904

Cat. No.	Length
87904	22" (559 mm)
87906	30" (762 mm)

WARNING: This is NOT an occupational protective belt. NOT for fall arrest or back support.

STEEL CONSTRUCTION



Bull-Pin Holders

- Riveted leather construction for long life.
- Holds all standard bull pins.



Cat. No.	Belt Connection	Belt Width	Overall Size
5417	slotted	up to 2" (51 mm)	3-1/4" x 11" (83 mm x 279 mm)
5417T	tunnel	up to 3-1/2" (89 mm)	3-1/4" x 12-1/4" (83 mm x 311 mm)

Erection Wrench Holders

- Leather construction.
- Has tool slots for two erection wrenches.
- Tunnel loop on Cat. No. 5459T and 5461T is riveted to assure long life.
- Holds erection wrenches and adjustable head construction wrench Cat. No. 3239.



Cat. No.	Belt Connection	Belt Width	Overall Size
5460	slotted	up to 2" (51 mm)	6" x 8-1/2" (152 mm x 216 mm)
5461T	cotton web tunnel	up to 2" (51 mm)	6" x 10" (152 mm x 254 mm)
5459T	tunnel	up to 3-1/2" (89 mm) or to slide over D-rings, buckles, and other accessories	6" x 9-1/2" (152 mm x 241 mm)

Construction Bars

- Provides extra leverage when positioning steel members and aligning bolt holes.
- Forged fit-up bar is pointed on one end.
- Chisel-end is at a 15° angle to give greater leverage.
- Gooseneck Bar (Cat. No. GN3243) chisel-end is at a 45° angle to give greater leverage.
- "TT" Series features tethering hole for working at height.



Round Bars

Cat. No.	Diameter	Length
3245	3/4" (19 mm)	30" (762 mm)
3246	7/8" (22 mm)	36" (914 mm)
3246TT*	7/8" (22 mm)	36" (914 mm)
3247	3/4" (19 mm)	24" (610 mm)
3248	7/8" (22 mm)	30" (762 mm)
Straight Chisel-End		
3241	3/4" (19 mm)	30" (762 mm)

*Has tethering hole

Hex Bars

Cat. No.	Hex Diameter	Length
3242	3/4" (19 mm)	30" (762 mm)
3243	7/8" (22 mm)	36" (914 mm)
3244	3/4" (19 mm)	24" (610 mm)
Straight Chisel-End		
3240	3/4" (19 mm)	30" (762 mm)
Gooseneck Bar		
GN3243	7/8" (19 mm)	29-1/4" (743 mm)





5459C

5459SLVR

Connecting Bar Holder with Lock Collar

- Lock Collar fits Klein® 7/8" (22 mm) connecting Bars (Cat. Nos. 3246 & 3248)
- Leather steel construction.
- Tunnel loop allows for weight distribution on belt.
- Fits belts up to 3-1/2" (89 mm) wide.
- Lock collar (Cat. No. 5459C) included; also available separately.

Cat. No.	Belt Connection	Belt Width	Overall Size
5459SLVR	tunnel loop	up to 3-1/2" (89 mm)	3" x 6-3/4" (76 mm x 171 mm)

Replacement Collar
5459C

⚠WARNING: Lock collar should ONLY be used on Klein 7/8" connecting bars. Lock collar must be installed on connecting bar before using holder.

Tool Tethers



TT2

TT1

- Keep your tools close at hand while working at height
- Allow for easy tool recovery in case of accidental drops
- Triple-locking carabiner for additional safety

Cat. No.	Maximum Load Capacity	Relaxed Length	Stretched Length
TT1	10 lbs (4.5 kg)	32' (813 mm)	60' (1.5 m)
TT2	15 lbs (4.5 kg)	32' (813 mm)	51' (1.3 m)



Always use choke hitch formation



Attach tether through tether hole when available



Always use a load bearing anchor or attachment point

⚠WARNING:

- Inspect for wear before each use.
- Do not use for human support.
- Maximum Working Capacity 10 lbs. (4.5 kg). Never connect over 5 lbs. (2.3 kg) to a person.
- Do not use around moving or rotating equipment.

⚠WARNING:

- Tether extends to length of 5' (1.5 m). Rig to avoid contact with objects below.
- Always ensure cinch remains snug while in use.
- Always attach carabiner end to anchor point.
- Do not attach tether back onto itself.
- Do not tie knots in tether.



Steel Bull Pins

Broad Head

- Forged, heat-treated steel increases efficiency by providing a larger striking surface.
- Angled head and smooth blending of radii increase strength and reduce the danger of chipping.
- Below the head, squared-off shoulders forged to provide a surface for applying wrench to loosen wedged bull pins.
- Added resistance to “mushrooming” permits longer use than conventional designs and the even taper reduces binding and hang-up.
- “TT” Series feature tether hole for working at height.

Standard and Barrel-Type Drift

- Machined from quality alloy steel.
- Heat-treated for strength, black oxide finish for rust resistance.



Cat. No.	Material	Top Dia.	Point Dia.	Length
Broad Head				
3255	Steel	1-1/4" (32 mm)	5/16" (8 mm)	13-3/4" (349 mm)
3255TT	Steel	1-1/4" (32 mm)	5/16" (8 mm)	13-3/4" (349 mm)
3256	Steel	1-1/16" (27 mm)	1/4" (6 mm)	10" (254 mm)
3256TT	Steel	1-1/16" (27 mm)	1/4" (6 mm)	10" (254 mm)
Standard				
3251	Steel	1-1/16" (27 mm)	3/8" (10 mm)	15" (381 mm)
3252	Steel	1-3/16" (30 mm)	7/16" (11 mm)	15" (381 mm)
3257	Steel	1-1/16" (27 mm)	3/8" (10 mm)	12" (305 mm)
3258	Steel	1-3/16" (30 mm)	7/16" (11 mm)	12" (305 mm)
3259	Steel	1-5/16" (33 mm)	7/16" (11 mm)	12" (305 mm)
3259TT	Steel	1-5/16" (33 mm)	7/16" (11 mm)	12" (305 mm)
3259TTS	Stainless Steel	1-5/16" (33 mm)	7/16" (11 mm)	12" (305 mm)
3265	Steel	1-1/4" (32 mm)	7/16" (11 mm)	12" (305 mm)
Barrel-Type Drift Pins				
3260	Steel	11/16" (18 mm)	5/16" (8 mm)	7-1/2" (191 mm)
3261	Steel	13/16" (21 mm)	7/16" (11 mm)	8" (203 mm)
3262	Steel	15/16" (24 mm)	1/2" (13 mm)	8" (203 mm)
3263	Steel	1-1/16" (27 mm)	9/16" (14 mm)	8" (203 mm)

Note: OSHA 1926.301 (c) specifically states: “Impact tools, such as drift pins, wedges and chisels, shall be kept free of mushroomed heads.”



3239

Adjustable-Head Construction Wrenches with Tether Hole



- Eliminates the need to carry several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle.
- Industrial black finish for corrosion resistance.
- Lanyard hole for easy tool tethering.

Cat. No.	Max. Size Capacity	Length
3227	1-5/16" (33 mm)	11" (279 mm)
3239	1-1/2" (38 mm)	16" (406 mm)



3238

1/2" – Drive Ratcheting Construction Wrench

- Accepts 1/2" (13 mm) square-drive hex socket.
- Reversible ratchet.
- Eliminates the need for carrying several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle for aligning bolt and/or rivet holes.
- Industrial black finish for corrosion resistance.


Cat. No.	Overall Length
3238	15" (381 mm)





Erection Wrenches

- Forged from select alloy steel to withstand high-leverage and heavy loads.
- Extra-heavy-duty head area gives maximum strength and durability.
- Continuous taper of handle makes lining up bolt holes easy and works on a range of bolt-hole sizes without binding.
- Extra-large hub area works on larger diameter holes better than other wrenches.
- Catalog number, bolt size and nominal opening size are stamped on every wrench for easy identification.
- "TT" Series feature tether hole to secure tool when working at height.



A - Bolt Size/Nominal Opening
 B - Head Width
 C - Overall Length

Cat. No.	Nut Type	Bolt Size	Nom. Opening	Head Width	Taper Diameter	Overall Length
3210	U.S. heavy	1/2"	7/8"	2-1/4"	7/8" to 3/16"	14-3/4"
3211	U.S. heavy	5/8"	1-1/16"	2-1/4"	7/8" to 3/16"	14-3/4"
3212	U.S. heavy	3/4"	1-1/4"	2-1/2"	1" to 1/4"	16-5/8"
3212TT	U.S. Heavy	3/4"	1-1/4"	2-1/2"	1" to 1/4"	16-5/8"
3213	U.S. heavy	7/8"	1-7/16"	3"	1-1/8" to 9/32"	17-3/8"
3213TT	U.S. Heavy	7/8"	1-7/16"	3"	1-1/8" to 9/32"	17-3/4"
3214	U.S. heavy	1"	1-5/8"	3-5/8"	1-1/8" to 1/4"	18"
3214TT	U.S. Heavy	1"	1-5/8"	3-5/8"	1-1/8" to 1/4"	18"
3219	U.S. regular	1/2"	3/4"	2-1/4"	7/8" to 8/16"	14-3/4"
3220	U.S. regular	1/2"	13/16"	2-1/4"	7/8" to 3/16"	14-3/4"
3221	U.S. regular	5/8"	1"	2-1/4"	7/8" to 3/16"	14-3/4"
3222	U.S. regular	3/4"	1-1/8"	2-1/2"	1" to 1/4"	16-5/8"
3223	U.S. regular	7/8"	1-5/16"	3"	1-1/8" to 9/32"	17-3/8"
3224	U.S. regular	1"	1-1/2"	3-5/8"	1-1/8" to 1/4"	18"
3231	utility	5/8"	15/16"	2-1/4"	7/8" to 3/16"	14-3/4"
3232	utility	3/4"	1-1/16"	2-1/2"	1" to 1/4"	16-5/8"



CONCRETE CONSTRUCTION



Grizzly™ Bar



64306

- A heavy, strong, multi-purpose tool that saves time and effort on the job.
- The 3" (76 mm) width protects concrete when stripping forms.
- Efficient blade angle and 55-1/2" (141 cm) total length provide high leverage as a crow bar, as well as a nail and spike puller.
- Blade is forged and hardened alloy with keyhole nail-pulling slot in center and "V" notch in tapered edge.
- Can be used to help align walls during tilt-up construction, to roll and align large pipe, to remove shingles and flooring, and for many other stripping and prying tasks.

Cat. No.	Overall Length
64306	55-1/2" (1410 mm)

⚠WARNING: Always wear approved personal protective equipment.

Rebar Hickeys

- Lightweight rebar hickey has exceptionally durable steel-alloy head and extra-strong handle to withstand extreme conditions.



64309

Cat. No.	Hickey Size	Bends Rebar Size	Head Type and Bending Angle	Handle Length
64309	1a	nos. 3 (.375" dia.), 4 (.500" dia.)	double 65° and 90°	24" (610 mm)
64310	2	no. 5 (.625" dia.)	single 65°	40" (1016 mm)
64311	3	no. 6 (.750" dia.)	single 65°	40" (1016 mm)
64312	4	nos. 7 (.875" dia.), 8 (1.00" dia.), 9 (1.128" dia.)	single 65°	60" (1524 mm)



27400



27450

Tie-Wire Reel

- Klein's redesigned tie-wire reel allows loading pre-coiled tie wire onto the reel without having to remove the cover.
- Rugged, lightweight reel is smooth aluminum alloy with wear parts made of steel.
- Designed for left or right hand use.
- Large, comfortable rewind knob.

Cat. No.	Diameter	Width
27400	6-1/4" (159 mm)	2-25/32" (71 mm)

Tie Wire Reel Pad

Cat. No.	Length	Width
27450	7" (178 mm)	7" (178 mm)



Load Rated Canvas Buckets

- Durable straight wall buckets are made of heavy-duty canvas to withstand the harshest job site conditions.
- Reinforced bottoms extend up the sides for added durability
- Web straps extend down the sides for additional strength
- The “No.” refers to the canvas weight with No. 1 being the thickest and No. 6 being the thinnest.

PROUDLY BUILT IN
USA
WITH GLOBAL COMPONENTS

**LOAD
RATED**



5104OCTO



Vinyl Bucket top
attaches with Velcro®



14" diameter accommodates
standard 5 gallon bucket on
5104CLR22 and 5104CLR17.

Cat. No.	Canvas Type	Load Rating	Extra Features	Diameter	Height
51TOP	N/A	N/A	attaches with Velcro®	12.5" (318 mm)	3.5" (89 mm)
5109	No. 6	75 lbs (34 kg)	black molded polypropylene bottom	12" (305 mm)	15" (381 mm)
5104	No. 4	100 lbs (45 kg)	inside pocket	12" (305 mm)	17" (432 mm)
5104OCTO	No. 1	100 lbs. (45 kg)	D-rings for tethering tools	12" (305 mm)	17" (432 mm)
5104VT	No. 1	100 lbs. (45 kg)	Velcro® closure	12" (305 mm)	17" (432 mm)
5104CLR17	No. 1	150 lbs. (68 kg)	zipper	14" (356 mm)	17" (439 mm)
5104CLR22	No. 1	150 lbs. (68 kg)	zipper	14" (356 mm)	22" (559 mm)

VELCRO® is a registered trademark of Velcro Industries B.V.

⚠️ WARNINGS: Completely close top before each use.

⚠️ WARNINGS:

- Inspect for damage before each use.
- Remove from service if bucket shows signs of wear.
- Never exceed the working load limit.



4-Pocket Tool Pouch

- Black leather construction.
- Riveted and stitched for extra durability.
- Includes knife snap.
- Slotted to fit belts up to 2" (51 mm) wide.



5119

Pliers, Folding Rule, Screwdriver, and Wrench Pouch

- Black leather construction.
- No exposed rivets in back.
- Riveted for long life.
- Four pockets for 7", 8", and 9" side-cutting pliers, most screwdrivers, 6' folding rules, and open-end wrenches from 9/16" to 13/16".
- Nickel plated alloy snap.
- Slotted to fit belts up to 2" (51 mm) wide.



5118C

Cat. No.	Overall Size
5119	6-1/2" x 8-1/2" (165 mm x 216 mm)

Cat. No.	Overall Size
5118C	6-1/2" x 11" (165 mm x 279 mm)

6-Pocket Tool Pouch

- One deep center pocket and 5 outside pockets plus a tape thong.
- Tunnel loop fits 2" (51 mm) belts.
- Heavy-duty reinforced bottom.



5241

8-Pocket Drill Pouch

- Fits battery and impact drills.
- Snap closure keeps drill in place.
- Outside pockets hold a variety of drill bits.
- Compatible with belts up to 2" wide.



5183

Cat. No.	Overall Size
5241	10-1/4" x 6-3/4" x 4" (260 mm x 172 mm x 102 mm)

Cat. No.	Overall Size
5183	3" x 7-1/4" (76 mm x 184 mm)

9-Pocket Small Maintenance Pouch

- Tunnel loop fits 2" (51 mm) belts.
- Easy 'grab and go' styling keeps your basic tools ready and right at hand.
- Includes a tape thong.



5240

Cat. No.	Overall Size
5240	1-1/2" x 10-1/4" (38 mm x 260 mm)

9-Pocket Tool Pouch

- Deep center pocket.
- Closed front pocket to carry small parts.
- Includes an array of pockets for various tools, plus a tape thong.
- Sturdy clip-on handle for convenient "pick up and go" mobility.
- Tunnel loop fits 2" (51 mm) belts.
- Padded shoulder strap included for hands-free carrying.



5242

Cat. No.	Overall Size
5242	9-1/2" x 7-1/2" x 4" (241 mm x 191 mm x 102 mm)



Knife Holder with Clip

- Holds knives up to 4.5" (145 mm) when closed.
- Magnetic flap closure.
- Metal clip for belt or pocket.



5248

Cat. No.	Overall Size
5248	5-1/2" x 2-1/2" x 1-1/8" (133 mm x 64 mm x 29 mm)

Tape Measure Holder with Tether Ring



- Elastic bottom and hook-and-loop closure ensure this holder will fit most 25' and 30' tape measures securely.
- Includes D-ring on top for tethering.
- Reinforced stitching to add strength.
- Cut out sides for easy access to tape.



5195TT

Cat. No.	Overall Size
5195TT	3" x 3.5" x 2" (76 mm x 89 mm x 50 mm)

15-Pocket Tool Pouch

- Heavy duty reinforced bottoms
- Features multiple pockets of various sizes, plus a tape thong
- Great for carrying a mix of tools and job site consumables
- Includes a padded shoulder strap for easy carrying, to use without a belt
- Tunnel loop fits 2 inch (51mm) belts



5243

Cat. No.	Overall Size
5243	11 -1/2" x 10" x 4-1/2" (292 mm x 254 mm x 114 mm)

Tool Pouch Apron

- Six pockets for parts and assorted tools.
- Includes pencil/marker pockets and a tape thong.
- Heavy duty reinforced bottoms so tools won't poke through.
- Adjustable belt fits 32" - 53" (1321 - 1346 mm) waists.



5244

Cat. No.	Overall Size
5244	10-1/2" x 19" x 1/2" (267 mm x 483 mm x 13 mm)

⚠ WARNING: This is NOT an occupational protective belt.


Tradesman Pro Tablet Backpack

- Fits 10" tablets with protective covers.
- 1680D ballistic weave for durability.
- Tall interior pockets for long screwdrivers.
- Hard, molded front pocket protects safety glasses.
- Front zipper pocket for small parts and tools.
- Mesh zippered compartment for cables and adapters.
- Orange interior for easy tool visibility.
- Multiple pockets sized specifically to fit all your tools for complete organization.
- Tough, durable molded bottoms to protect from the elements.



55603

Cat. No.	Overall Size	Pockets
55603	14" x 7" x 18-1/2" (356 mm x 178 mm x 475 mm)	25



ACSR Ratcheting Cable Cutters

- High-leverage ratcheting mechanism for easier cutting.
- Quick-release lever opens blades easily in every cutting position (allows removal of the cable before completion of cut).
- Hardened steel cutting blades for long lasting strength and sharpness.
- Tools can be locked when not in use.
- Cat. No. 63800ACSR features cutting inserts that are easily replaced by simply removing 3 screws per blade.
- Plastic covered handles with hand guards for comfort and firm grip.



MCM Maximum Cable Capacity

Cat. No.	ACSR	Aluminum	Copper	Guy Strand	Handle Color	Overall Length
63607	336 MCM (170 mm ²)	600 MCM (300 mm ²)	400 MCM (185 mm ²)	—	yellow	10-1/4" (260 mm)
63800ACSR	477 MCM (273 mm ²)	1-1/4" (32 mm)	1" (25 mm)	1/2" (13 mm)	red	13-3/4" (349 mm)

Replacement parts available (blades, handles, springs, pawl sets and release plates).

Ratcheting ACSR Cable Cutter – Heavy-Duty

- Ratchet-action design provides maximum leverage with minimum effort.
- Blade-advance knob for fast rotation of the blade to engage the cable.
- Quick-release mechanism allows for removal of the cable or rod before completion of the cut, if desired.
- Not designed for cutting EHS guy strand or reinforcement rod.
- Cuts steel and ACSR.
- Forged, heat-treated, shear-type blades, plus 17" (432 mm) long fiberglass handles with heavy duty grips for comfort and slip resistance.



Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	Steel Cable-Cutting Maximum Capacity
63700	28" (711 mm)	2-1/4" (57 mm) diameter 750 MCM (1-3/8" dia.) (35 mm) copper or aluminum	1-1/4" (32 mm) dia. ACSR, ACAR 7/16" (11 mm) dia. common guy strand 5/8" (16 mm) dia. steel wire rope 1/2" (13 mm) dia. steel rod (C.R.S. SOFT)





63050

High-Leverage Cable Cutters

- High-leverage design for exceptional cutting capability.
- Precision, one-hand shearing action.
- Cable-gripping shear-type jaws.
- Perfect for working in confined spaces.
- Can be carried in most tool pouches.

Cat. No.	Maximum Cable Cutting Capacity	Handle Color	Overall Length
63050	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable	red	9-1/2" (241 mm)



63041

Standard and Communication Cable Cutter

- Lightweight, yet efficient shear-type cable cutters.
- Exceptionally strong fiberglass handles with heavy vinyl grips for comfort and slip resistance.
- Heavy-duty pins in head serve as blade-stops.
- Jaws are forged tool steel with black-oxide finish for long life.
- Beveled tips assure positive mating, and hinge on a rugged bolt with a pin-set nut to maintain proper blade tension.
- Makes a clean, even cut for ease in fitting lugs and terminals.

Cat. No.	Soft Cable-Cutting Maximum Capacity	MCM Cable-Cutting Maximum Capacity	Overall Length
63041	1-3/8" (35 mm) diameter	500 copper, 750 aluminum	25-1/2" (648 mm)



Ratcheting Cable Cutter

- High-leverage ratcheting for single-handed cutting of copper and aluminum cables, leaving no burrs or sharp edges.
- Two-step ratchet mechanism requires fewer strokes per cut.
- Open jaw design works in confined spaces.
- Quick release lever opens blades easily in every cutting position. (Allows removal of the cable before completion of cut).
- Hardened steel cutting blades for lasting strength and sharpness.
- Locking lever keeps handles closed for easy transport; fits in a toolbox or bag.



63711

MCM Maximum Cable Capacity

Cat. No.	Copper	Aluminum	ACSR	Communication Cable	Overall Length	Handle Color	Weight
63711	600 MCM (300 mm ²)	750 MCM (400 mm ²)	—	1-1/8" (28 mm)	11-1/2" (292 mm)	red	2.00 lbs.

Replacement parts available (blades, handles, springs, pawl sets and release plates).

WARNING: Do NOT cut steel or ACSR.



Steel Handled Bolt Cutters

- All-purpose, center-cut jaws
- Forged, alloy tool steel jaws are precision ground for sure, efficient cutting and long life.
- Lock plate reinforcement prevents jaw bolts from loosening or turning, keeping jaws in correct alignment.
- One adjustment realigns cutting edges.
- 3-point toggle joint multiplies 50 lbs. of hand pressure on handles to 4,000 pounds at cutting jaws.
- NOT for cutting cable.



63342

63314

Cat. No.	Overall Length	Soft & Medium Cutting Max. Capacities*	Hard Material Cutting Max. Capacities**
63314	14" (356 mm)	5/16" (8 mm)	3/16" (5 mm)
63318	18" (457 mm)	3/8" (10 mm)	1/4" (6 mm)
63324	24" (610 mm)	7/16" (11 mm)	5/16" (8 mm)
63330	30" (762 mm)	1/2" (13 mm)	3/8" (10 mm)
63336	36" (914 mm)	9/16" (14 mm)	7/16" (11 mm)
63342	42" (1067 mm)	11/16" (18 mm)	1/2" (13 mm)

Heavy-Duty Ratcheting Bolt Cutter

- Cuts 1/2" utility-grade guy strand, 3/8" EHS
- Spring-loaded cable retention hook snaps onto the cable in one hands-free motion and keeps strands between cutting blades
- Long handles provide leverage when cutting
- Lockplate reinforcement prevents jaw bolts from loosening or turning, keeps jaws in correct alignment




63RBCHD

Cat. No.	Cutting Capacity	Up to HRC	Overall Length
63RBCHD	1/4" - 1/2" (12.7 mm) Guy Strand up to 3/8" (9.5 mm) EHS	Rockwell C31 Rockwell C42	31" (78 cm)

*As defined by ASTM A475-98, 1/2" utility grade 7-strand guy strand has minimum breaking strength of 25,000 lbs (11,339.81 kg). 3/8" EHS 7-strand has minimum breaking strength of 15,400 lbs (6,985 kg).


⚠ WARNING: Do NOT cut steel or ACSR.





JOURNEYMAN™ Sheet Metal Snips

These cutting and notching snips make it easy to work with sheet metal. Soft touch grips with Klein Kurve® handles provide natural hand positioning for maximum control and comfort. Serrated steel blades are forged for superior strength. The Tip-Ident® feature on each handle end make for easy identification. Self-opening latches keep the blades securely shut when not in use. Available in Aviation, Bulldog, Right-Angle and Offset styles.



Cat. No.	Cutting Pattern	Type	Cutting Length	Color Code	Overall Length	Cutting Capacity: Cold Rolled Steel/Stainless
J2103S	Notch / Straight	Aviation, Bulldog	7/8" (22.22 mm)	Yellow/Black	9-7/16" (239.71 mm)	16 gauge/18 gauge
J1102S	Straight / Wide Curves	Aviation	1-1/2" (38.1 mm)	Yellow/Black	10-1/16" (255.58 mm)	18 gauge/22 gauge
2100L	Left / Straight	Offset	1-1/4" (31.75 mm)	Red/Black	9-1/2" (241.3 mm)	18 gauge/22 gauge
J2101R	Right / Straight	Offset	1-1/4" (31.75 mm)	Green/Black	9-1/2" (241.3 mm)	18 gauge/22 gauge
J2104L	Left Curves / Tight Circles / Straight	Upright	1-1/4" (31.75 mm)	Red/Black	7-15/16" (201.61 mm)	24 gauge/28 gauge

Auto-Loading Folding Retractable Utility Knife

- Rugged, heavy-duty and durable construction.
- Auto-loading blade for faster and safer blade changes.
- High quality triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- Internal blade storage holds and includes 3 blades.
- Lock release to close knife.
- Equipped with belt clip.



44130




Cat. No.	Length Closed	Overall Length w/Blade
44130	4.25" (108 mm)	6.625" (168.3 mm)

Folding Utility Knife

- Push button to easily open and close.
- Rugged, heavy-duty and durable construction.
- Contains a wire stripping notch.
- High quality, triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- Bright orange handle color makes this knife easy to find in a tool bag or pouch.



44131



Cat. No.	Length Closed	Overall Length w/Blade
44131	4.125" (104.8 mm)	6.375" (162 mm)

Klein Kurve™ Retractable Utility Knife

- Rugged, heavy-duty and durable construction.
- Now with a wire-stripping notch.
- High quality, triple ground blades stay sharp longer.
- Rubber grips for improved control and comfort.
- Designed for improved cutting ability.
- Internal blade storage includes and holds 6 blades.



44133



Cat. No.	Length Closed	Overall Length w/Blade
44133	6.875" (175 mm)	7.0" (178 mm)

Camouflage Assisted-Open Folding Utility Knife

- Realtree Xtra® Camo design handle with rubber grip and TPR overmold.
- Rugged, heavy-duty and durable construction.
- Spring-assisted opening with dual thumb knob for right-or left-handed use.
- Blade locks when in closed position.



44135



Realtree-XTRA Camouflage Design © 2012 of Jordan Outdoor Enterprises, Ltd., all rights reserved.

Cat. No.	Length Closed	Overall Length w/Blade
44135	4.44" (113 mm)	7.0" (178 mm)



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.



Self-Retracting Utility Knife

- Rugged, heavy-duty and durable construction.
- Wire-stripping notch.
- Safety yellow handle for greater visibility.
- Blade removal/insertion without disassembly.



44136

Blade retracts fully into housing when cut is complete.

Cat. No.	Length Closed	Overall Length w/Blade
44136	5.0" (127 mm)	5.75" (146 mm)

Small Pocket Knife

- Satin finish drop point blade.
- Black aluminum handle for corrosion resistance.
- Lock back secures blade in open position.



44142

Cat. No.	Blade Length	Open Length
44142	3-1/2" (89 mm)	6-3/4" (171 mm)

Folding Pocket Knife

- Satin finish drop point blade.
- Liner lock secures blade in open position.
- Silver aluminum handle for corrosion resistance.



44144

Cat. No.	Blade Length	Open Length
44144	4" (102 mm)	8" (203 mm)

Electrician's Pocket Knife

- Satin finish drop point blade.
- Liner lock secures blade in open position.
- Anodized aluminum handle for corrosion resistance.



44201

Cat. No.	Blade Length	Open Length
44201	3-3/4" (95 mm)	8" (203 mm)

Drop-Point Blade Pocket Knife

- 440A stainless steel drop point blade.
- Liner lock secures blade in open position.
- Rubberized handle grip.
- Lanyard hole for tethering.
- Aluminum handle for corrosion resistance.
- Dual thumb studs for one-hand open.
- Deep pocket/low carry clip.



44220

Cat. No.	Blade Length	Open Length
44220	3-1/2" (89 mm)	8-1/4" (209 mm)

Realtree Xtra™ Camo Tanto-Blade Pocket Knife

- Tanto blade for piercing.
- Straight edge for slicing.
- Serrated edge for tearing/ripping.
- Liner lock secures blade in open position.
- Rubberized handle grip.
- Deep pocket/low carry clip.
- Lanyard hole for tethering.
- Dual thumb studs for one-hand open.



44222



Realtree-XTRA Camouflage Design © 2012 of Jordan Outdoor Enterprises, Ltd., all rights reserved.

Cat. No.	Blade Length	Open Length
44222	3-1/2" (89 mm)	8-1/8" (206 mm)

Bi-Metal Hole Saws

- Optimized for cutting steel including stainless steel.
- Cuts precise holes in stainless steel and mild steel, drywall, ceiling tile, laminates, wood and plastic.
- Longest lasting, fastest cutting blade on the market.
- Heavy-duty steel construction includes 5 mil back plate to withstand abuse.
- The smallest hole saws feature hex-shaped base for easy removal from arbor.



Cat. No.	Saw Diameter	Pipe Tap Size*	Pipe Entrance Size**	For use with Arbor No.
31914	7/8" (22 mm)	3/4" (19 mm)	1/2" (13 mm)	31905
31918	1-1/8" (29 mm)	1" (25 mm)	3/4" (19 mm)	
31922	1-3/8" (35 mm)	-	1" (25 mm)	
31928	1-3/4" (44 mm)	1-1/2" (38 mm)	1-1/4" (32 mm)	31906
31932	2" (51 mm)	-	1-1/2" (38 mm)	
31940	2-1/2" (64 mm)	-	2" (51 mm)	
31944	2-3/4" (70 mm)	-	-	
31948	3" (76 mm)	-	2-1/2" (64 mm)	
31958	3-5/8" (92 mm)	-	3" (76 mm)	
31972	4-1/2" (114 mm)	-	4" (102 mm)	
31900	6-3/8" (162 mm)	-	6" (152 mm)	

* Pipe Tap Size – The sizes listed provide the necessary information whenever a pipe is to be threaded into tanks, boilers, etc. To secure the best results, the hole should be reamed before tapping with a reamer having a taper of 3/4" per foot.
 ** Pipe Entrance Size – The sizes listed provide the necessary information for any given pipe size to have sufficient clearance to pass through beams, walls, bulkheads, etc.

Electrician's Hole Saw Kit

- Optimized for cutting steel. Also cuts stainless steel.
- Cuts precise holes in stainless steel and mild steel, drywall, ceiling tile, laminates, wood and plastic.
- Longest lasting, fastest cutting blade on the market.
- Heavy-duty steel construction includes 5 mil back plate to withstand abuse.
- Hex-shaped base for easy removal from arbor.
- Contains the most popular sizes for basic electrical work.
- All components are packed in a rust-proof, molded plastic carrying case.



Cat. No.	Set Contains			
31902				
	Hole Saws		Arbors	
	Cat. No.	Size	Cat. No.	Size
	31914	7/8" (22 mm)	31905	3/8" (10 mm)
	31918	1-1/8" (29 mm)	31906	3/8" (10 mm)
	31922	1-3/8" (35 mm)		
	31928	1-3/4" (44 mm)		
	31932	2" (52 mm)		
	31940	2-1/2" (64 mm)		



NOTE: Read and follow safety instructions in power tool owner's manual.



Hole-Saw Arbors and Accessories

- Cat. No. 31905 is for use with all Klein hole saws.
- Cat. No. 31906 is for use with Klein hole saws 1-3/8" to 6-6/8" (35 mm- 162 mm).
- Fast and easy to engage and disengage hole saws.
- Steel construction for long life.
- 118° split point pilot bits.
- 31905 includes arbor adaptor for 5/8"-18.
- Hardened mandrels for long thread life.

Cat. No.	Shank Style	Pins	Shank Size	Electric Drill Size	Thread Size
31905	hexagonal	N	3/8" (10 mm)	1/2" and larger	1/2" - 20
31906	hexagonal	Y	7/16" (11 mm)	1/2" and larger	5/8" - 18
Replacement Pilot Drills for Hole-Saw Arbors					
31907	1/4" Replacement Pilot Drill Bit, 1/4" x 3-1/4"				



Double-Fluted High-Speed Step Drill Bits

High-visibility silver step rings!

- Faster drilling than single flute bits.
- Easy-to-read step rings save time when drilling common holes.
- Fast-starting, non-walking drill tip.
- Thick, extra-long 3/8" hex shank provides a firm, positive grip in the drill and won't spin out.

Cat. No.	Quick Reference	No. of Holes	Increment	Hole Size Range
KTSB01	#1	13	1/32"	1/8" - 1/2" (3 mm - 13 mm)
KTSB03	#3	9	1/16"	1/4" - 3/4" (6 mm - 19 mm)
KTSB11	#11	2	-	7/8" - 1-1/8" (22 mm - 29 mm)
KTSB14	#14	12	1/16"	3/16" - 7/8" (5 mm - 22 mm)
KTSB15	#15	3	-	7/8", 1-1/8", 1-3/8" (22, 29, 35 mm)



Wood Boring Bits with Screw Point

Easier to control and adjust shape on the fly.

- Superior to auger bits.
- Easy-to-sharpen blades.
- Easy-to-replace pilot screw shaft spin out.
- New low-torque design greatly reduces the wrist fatigue from standard auger bits.
- Unique head shape minimizes chatter while drilling versus ordinary paddle bits.

Cat. No.	Hole Size	Shaft Dia.	Hex End	Shaft Length
53932	7/8" (22 mm)	3/8" (9.5 mm)	5/16" (8 mm)	6" (152 mm)
53934	1-1/8" (29 mm)			
53936	1-3/8" (35 mm)			
53938	Replacement Shaft			



NOTE: Read and follow safety instructions in power tool owner's manual.



818-16

Curved-Claw Hammers – Heavy-Duty

- Durable plastic-alloy jacketing helps to protect neck from fraying and splintering if incorrectly struck or overstruck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Curved claw gives maximum nail-pulling leverage.

Cat. No.	Head Weight	Overall Length
818-16	16 oz. (454 g)	13" (330 mm)
818-20	20 oz. (567 g)	14" (356 mm)



823-48

Hand-Drilling Hammer

- Extra-heavy, forged steel head, hardened and tempered.
- Short handle for working in close quarters.
- Select hickory handle, triple-wedged and lacquered to withstand weather.
- Special handle treatment removes handle moisture and replaces it with oil to help eliminate the effects of extreme temperatures.

Cat. No.	Head Weight	Overall Length
823-48	48 oz. (1361 g)	10" (254 mm)



819-03

Non-Sparking Hammers

- Non-sparking, non-marring brass-head hammers.
- Fiberglass handle includes TPR overmold for extra comfort and shock absorption.
- Built-in overstrike protector absorbs shock and vibration when overstrike occurs.
- Large sweep at base prevents loss of grip.
- Head is securely epoxied to prevent detachment.
- Does not contain beryllium.

Cat. No.	Head Weight	Overall Length
819-03	3 lbs. (1021 g)	15.75" (400 mm)
819-04	4 lbs. (1.8 g)	16" (406 mm)



7HBRFRH14

Brass Sledge Hammer

- Used in non-sparking environments or to avoid damage to struck objects.
- Head forged from brass for softer, non-damaging blow.
- Head is pinned to handle as well as epoxied to prevent head coming off.
- Comfortable, thick rubber grip handle for better protection from shock and vibration.
- Handle includes both overstrike protection and large sweep at base to prevent loss of grip.
- This product must be maintained in accordance with Australian standard AS 3797:1991.

Cat. No.	Head Weight	Overall Length
7HBRFRH04	4 lbs. (1.81 kg)	16" (406.4 mm)
7HBRFRH07	7 lbs. (3.18 kg)	32" (812.8 mm)
7HBRFRH10	10 lbs. (4.53 kg)	36" (914.4 mm)
7HBRFRH14	14 lbs. (6.35 kg)	36" (914.4 mm)





56220

Headlamp

- Anti-slip silicone strap keeps headlamp securely fastened to hard hat.
- Strap comes pre-adjusted for quick fit to hard hat.
- 45-degree tilt for varied beam direction to point light where it is needed most.



Cat. No.	Lumens	Run Time	Drop Height	Batteries
56220	150 / 50	6 hrs / 10 hrs	6 ft.	3xAAA



51425

Klein Kleaners® Hand Cleaning Towels

Cat. No.	Container Size
51425	72-count bucket



Hats and Caps & Advance® Cap

- Different styles to fit your needs meet or exceed ANSI.
- Third Party Certified by Safety Equipment Institute.
- Glaregard™ under the brim of Advance® Caps reduces reflective glare.

All backs contain the Klein logo with American flag. Logo color varies depending on shell color.

Cat. No	Front Logo	Color
V-Gard® Hard Hats Meet ANSI Z89.1-2003 and CSA Z94.1-2005, Class E		
60028	none	white
60030	none	blue
60031	lineman	white
Standard Hard Caps Meet ANSI Z89.1-2003, Class E		
60009	none	white
60010	none	yellow
60011	none	blue
Advance® Caps Meet ANSI Z89.1-2003, Class C		
60025	none	white
60027	none	blue

Glaregard™, Advance®, and V-Gard® are registered trademarks of MSA, the safety company.

Scope of Z89.1 - 2014 American National Standard for Head Protection

TYPE I (Top Impact) Helmets intended to reduce the force of an impact to the top of a wearer's head.

TYPE II (Top and Lateral Impact) Helmets intended to reduce the force of an impact resulting from a blow received off-center or to the top of a wearer's head.

Electrical Performance

CLASS E (Electrical) Helmets intended to reduce the danger of exposure to high-voltage electrical conductors, proof-tested at 20,000 volts.

CLASS G (General) Helmets intended to reduce the danger of exposure to low-voltage electrical conductors, proof-tested at 2,200 volts.

CLASS C (Conductive) Helmets not intended to provide protection from electrical conductors.



60053

60046

Protective Eyewear


- Meets the traffic signal color recognition requirements of ANSI Z80.3-1996.

*SCT® = Spectrum Control Technology



Cat. No.	Frame Color	Lens Color	Environment	Visual Light Transmitted	Accidental Arc Protection
60046	black	dark gray	outdoor	10%	No
60047	black	SCT* gray	outdoor	15%	Yes
60049	black	amber	indoor/ outdoor	90%	No
60053	black	clear	indoor	92%	No
60054	royal blue	clear	indoor	92%	No
60055	black	espresso	outdoor	15%	No
Frameless					
60056	black	clear	indoor	92%	No
60057	black	espresso	outdoor	15%	No

Lens Color



60080

Disposable Dust Masks

Cat. No.	Description
60080	box of 50 disposable dust masks

WARNING: Dust masks are NOT SUITABLE for use against toxic or hazardous air contaminants. If there is any doubt, consult an industrial hygienist.



58000

Barricade and Warning Tapes

Cat. No.	Description	Length
58000	CAUTION – CAUTION legend w/blk letters/yellow background	200' (61 m)
58001	CAUTION – CAUTION legend w/blk letters/yellow background	1000' (305 m)
58002	CAUTION – BURIED ELECTRIC LINE legend w/blk letters/red bk-grnd	200' (61 m)
58003	CAUTION – BURIED ELECTRIC LINE legend w/blk letters/red bk-grnd	1000' (305 m)



45201

Lockouts with Interlocking Tabs

- Specifically designed for locking out power sources such as disconnects, switches, and panel boxes.
- Double interlocking hasp of tempered steel with patented interlocking tabs for extra security.
- Holes will accept up to 5/16" (8 mm) diameter shackles.

Cat. No.	Description
45200	1" (25 mm) lockout
45201	1-1/2" (38 mm) lockout

WARNING: Use only in accordance with OSHA requirements.

Cowhide Work Gloves

- Premium cowhide, soft and form-fitting for maximum comfort.
- Gunn cut with seams away from wear surfaces.
- Inseam index finger.
- Shirred-elastic wrist back.
- Natural light-tan color.



40022

	Medium	Large	Extra-Large
Cat. No.	40021	40022	40023
Pile Lining			
Cat. No.	40016	40017	40018

Cowhide Driver's Gloves

- Tough, durable, sueded cowhide leather.
- Easy-action thumb – unique design allows leather to conform to your thumb and hand (Cat. Nos. 40003, 40004, 40006).
- Thermolite® lining for warmth (Cat. Nos. 40014 and 40015).
- Gunn cut with seams away from wear surfaces.
- Lap-seam index finger and shirred-elastic wrist back.
- Gray color.



40006

	Small	Medium	Large	Extra-Large
Cat. No.	40003	40004	40006	–
Pile Lining				
Cat. No.	–	–	40014	40015

Electrician's Gloves

- Durable construction allows flexibility.
- Features slip resistant construction.
- Spandex material is breathable and comfortable to wear all day.
- Constructed with a reinforced area at the base of the thumb.
- Elastic cuff for secure and comfortable fit.
- Index fingers are wrapped with slip-resistant material.
- Extended cuff for easy on/off.



40072

	Medium	Large	Extra-Large
Cat. No.	–	40072	40074

Lineman Work Gloves

- 4" Neoprene cuff with side vents.
- Soft grain leather construction with reinforced leather patches.
- Double-row padded knuckle for durability.
- Black spandex back with Klein lineman logo patch.



40080

	Medium	Large	Extra-Large	2XL
Cat. No.	40080	40082	40084	40086

Medium & Long-Cuff Gloves

- Gunn cut with seams away from wear surfaces.
- Wing thumb, seamless index finger, elastic wrist-back strap.
- Lined palm and fingers.
- Heavy sueded leather (Cat. No. 40008).
- Long-cuff gloves feature:
 - Soft, flexible, top-grain cowhide leather.
 - Leather fingers, palm, pull, and knuckle strap.
 - Rubberized, waterproof, bell gauntlet cuff 5" (127 mm) long.



40008

Cat. No.	Style	Size
40008	Medium-cuff	Large
40010	Long-cuff	Large
40012	Long-cuff	Extra-Large

Heavyweight Jersey Gloves

- Soft, comfortable, general-purpose gloves.
- Made of 100% cotton jersey.
- Dark-brown color.



40002

Cat. No.	Size	Features
40002	fits most hand sizes	knit wrist

Extreme Gloves

- PORON® padding material in the palm to absorb impact and vibration.
- Rubberized fingertips for extra grip.
- Wrist closure with hook and loop secures fit.



40217

	Medium	Large	Extra-Large
Cat. No.	40217	40218	40219

Utility Gloves

- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.



40206

	Medium	Large	Extra-Large
Cat. No.	40205	40206	40207

Camouflage Gloves

- Mossy Oak® Break-Up Infinity™ pattern.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.



40209

	Medium	Large	Extra-Large
Cat. No.	40208	40209	40210

Cold Weather Pro Gloves

- Palm and fingers lined with Thinsulate™ C40.
- Water resistant nylon back lined with Thinsulate™ C100.
- Durable rubberized palm provides water resistance and grip with 2mm EVA foam padding for impact protection.
- 5 mm EVA foam knuckle for impact protection and comfort.



40212

	Medium	Large	Extra-Large
Cat. No.	40211	40212	40213

Grip Gloves

- Armortex® rubberized grip on the fingers with reinforced synthetic leather palms and thumb for ample grip in both wet and dry conditions.
- PORON® padding material in the palm to absorb impact and vibration.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.
- Flexible yet impact absorbing thermo plastic rubber (TPR) protects the fingers and back of the hand.



40214

	Medium	Large	Extra-Large
Cat. No.	40214	40215	40216

Leather Gloves

- Genuine professional grade leather.
- Flexible yet impact absorbing thermo plastic rubber (TPR) protects the fingers and back of the hand.
- Moisture wicking and breathable Trek Dry™ stretch material on top with sponge foam and tricot lining for maximum comfort.
- Machine washable.



40221

	Medium	Large	Extra-Large
Cat. No.	40220	40221	40222



GO MOBILE!
Text "KLEIN"
to 37527 for
mobile
alerts



SUBSCRIBE
to Klein's YouTube channel



TRADESMAN TV
for tool reviews from
fellow tradesmen

STAY CONNECTED

TRADESMAN CLUB



JOIN THE TRADESMAN CLUB
at www.kleintradesmanclub.com for
the latest products, innovations and
chances to win free tools



**ELECTRICIAN
OF THE
YEAR**

A DECADE OF DEDICATION

GET REWARDED FOR YOUR LOYALTY!



Get 1 point for each dollar spent. Use your points to redeem for Klein merchandise



**KLEIN
TOOLS** 
For Professionals... Since 1857™



www.kleintools.com

© 2016 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96475 10/16 Rev.A