



orbit[®]
Orbit Industries, Inc.



TITLE 24
COMPLIANT 

VENTILATION FANS & FANLIGHTS

Summer 2014 Catalog

*“ Serene comfort
for your home ”*



INNOVATIVE VENTILATION SOLUTIONS

QUIET

Our fans feature the best and quietest fan motors in the ventilation market with optimal comfort that lasts up to 60,000 hours.

EASY INSTALLATION

All fans are quick and easy to install with our innovative snap-in wiring connections and built-in mounting tabs that help save you time.

SELECTION

Builders and homeowners can choose from fans with LED lights, DC motors, or motion and humidity sensors for any installation.

ENERGY SAVINGS

Orbit's ventilation fans save up to 50% on utility costs and are Energy Star certified, UL and cUL listed.

Featuring innovative technology, Orbit's ventilation fans deliver quality performance that contractors and homeowners rely on.

With a wide range of solutions which include motion and humidity sensors and an efficient DC motor, our fans will keep your home safe from harmful pollutants and excess moisture. Protect your home and breathe better by choosing one of our exceptional ventilation fan models.



TITLE 24
COMPLIANT 

orbit
Orbit Industries, Inc.

TABLE OF CONTENTS







PRODUCTS	SERIES	Model	CFM	Sones	Duct	Pg.
	Universal Deluxe Fans With DC Motor & Motion Sensor	ODU814M	80 - 140	0.3 - 1.1	4"&6"	1
	Universal Deluxe Fans With DC Motor & Humidity Sensor	ODU814H	80 - 140	0.7 - 1.1	4"&6"	2
	Universal Deluxe Fanlights With DC Motor & Humidity Sensor	ODU814LH	80 - 140	0.7 - 1.1	4"&6"	2
	Universal Deluxe LED Fanlights With DC Motor & Humidity Sensor	ODU814LLH	80 - 140	0.7 - 1.1	4"&6"	2
	Deluxe Fans With Humidity Sensor	OD80H	80	0.7	4"	3
	Deluxe Fans With Humidity Sensor	OD110H	110	0.6	4"	
	Deluxe Fanlights With Humidity Sensor	OD80LH	80	0.7	4"	3
	Deluxe Fanlights With Humidity Sensor	OD110LH	110	0.6	4"	
	Deluxe LED Fanlights With Humidity Sensor	OD80LLH	80	0.7	4"	3
	Deluxe LED Fanlights With Humidity Sensor	OD110LLH	110	0.6	4"	
	Deluxe Recessed Fanlights	OE80RL	80	1.0	4" & 5"	4
	Deluxe Recessed LED Fanlights	OE80RLL	80	1.0	4" & 5"	4
	Deluxe Fans	OD80	80	0.8	4"	5
		OD90	90	1.0	4"	
		OD110	110	1.5	4"	
		OD120	120	2.0	4"	
	Deluxe Fanlights	OD80L	80	0.5	4"	5
		OD90L	90	0.7	4"	
		OD110L	110	1.2	4"	
		OD120L	120	1.5	4"	

TABLE OF CONTENTS

PRODUCTS	SERIES	Model	CFM	Sones	Duct	Pg.
	Deluxe Heat Fan Light	ODHFL110	110	0.6	4" & 6"	6
	Economy Plus Fans	OEP80	80	1.3	4"	7
		OEP90	90	1.5	4"	
		OEP110	110	2.0	4"	
	Economy Plus Fanlights	OEP80L	80	1.0	4"	7
		OEP90L	90	1.1	4"	
		OEP110L	110	1.0	4"	
	Economy Fans	OE50	50	3.0	3"	8
		OE70	70	3.5	4"	
		OE80	80	4.0	4"	
	Standard Plus Fans	OSP50	50	3.5	3"	9
		OSP70	70	3.5	4"	
	Standard Plus Fanlights	OSP70L	70	3.5	4"	9
	Standard Fans	OS50	50	3.2	4"	10
		OS70	70	4.0	4"	
	Standard Heat Fan Light	OEHFL70	70	4.0	4"	11
	Contractor Packs					12
	Wiring Devices					14
	Fan Accessories					15

UNIVERSAL DELUXE SERIES

DC Motor & Motion Sensor

Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4" or 6"** polymeric collar with lightweight built-in back draft damper
- IC Rated up to R40 insulation




See Fan Curve (1) on Pg.16

Motor

- Power rating of 120V / 60Hz
- Permanently lubricated motor
- Energy efficient, brushless **two speed DC motor** for low speed continuous ventilation from 30 to 80 CFM
- Quick installation of motor and impeller assembly
- Built-in dip switch to adjust high fan speed setting from 80 to 140 CFM
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when used with a GFCI branch circuit

Grille



Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion clips included for easy mounting

Motion Sensor

- Activates higher motor speed and delayed timer
- Adjustable timer from 5 to 60 minutes

Warranty

- 2 year limited warranty



Cat. No.		ODU814M				
Static pressure	Inches w.g.	0.1"				
Duct diameter	Inches	4" & 6"				
Air volume	CFM	80	90	110	120	140
Noise	Sone	0.3	0.3	0.6	0.8	1.1
Power consumption	Watts	9	9	10	10	11
Energy efficiency	CFM/Watts	8.9	10	11	12	14
Power rating	V/Hz.	120/60				

UNIVERSAL DELUXE SERIES

DC Motor & Humidity Sensor

Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4" and 6"** round duct with built-in draft damper
- IC Rated up to R40 insulation

Motor and Blower

- Power rating of 120V / 60Hz
- Permanently lubricated, quick installation motor
- Energy efficient, brushless **two speed DC motor** for low speed continuous ventilation from 30 to 80 CFM
- Built-in dip switch to adjust high fan speed setting from 80 to 140 CFM
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

Humidity Sensor

- Adjustable from 50 to 100% relative humidity
- Adjustable timer from 5 to 60 minutes

Warranty

- 2 year limited warranty

Lighting

FANLIGHTS

Included:
1 - 23 Watt GU24 Compact Fluorescent Lamp & 1 - 4 Watt Incandescent Lamp



LED FANLIGHTS

Included:
10 Watt LED Lamp



ODU814H



ODU814LH & ODU814LLH

See Fan Curve (1) on Pg.16



TITLE 24 COMPLIANT

Cat. No.	FANS				FANLIGHTS		LED FANLIGHTS		
	ODU814H				ODU814LH		ODU814LLH		
Static pressure	Inches w.g.	0.1"							
Duct diameter	Inches	4"				6"			
Air volume	CFM	80	90	110	120	90	110	120	140
Noise	Sone	0.7	0.7	0.6	1.2	0.3	0.5	0.8	1.1
Power consumption	Watts	5.5	7.0	11.9	13.0	5.5	10.0	11.5	14.5
Energy efficiency	CFM/Watts	14.55	12.86	9.24	9.23	16.36	11.00	10.43	9.66
Power rating	V/Hz.	120/60							
Weight	lbs	10.6							
Master Qty.		1							

DELUXE SERIES

Humidity Sensor

Housing Dimensions

- 11-3/8" L x 10-1/2" W x 7-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4" and 6"** round duct with built-in draft damper
- IC Rated up to R40 insulation

Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor
- Quick installation of motor and impeller assembly
- Low RPM for quiet operation
- Built-in overload disconnect for safety and longer motor life
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Modern and elegant design
- Durable Polymeric Resin
- Torsion spring clips included for easy mounting

Humidity Sensor

- Adjustable from 50 to 100% relative humidity
- Adjustable timer from 5 to 60 minutes

Warranty

- 2 year limited warranty

Lighting

FANLIGHTS

Included:
1 - 23 Watt GU24 Compact Fluorescent Lamp & 1 - 4 Watt Incandescent Lamp



LED FANLIGHTS

Included:
10 Watt LED Lamp



OD80H & OD110H



OD80LH & OD110LH
OD80LLH & OD110LLH

See Fan Curve (2) on Pg.16



TITLE 24 COMPLIANT

		FANS		FANLIGHTS		LED FANLIGHTS	
Cat. No.		OD80H	OD110H	OD80LH	OD110LH	OD80LLH	OD110LLH
Static pressure	Inches w.g.	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"
Air volume	CFM	80	110	80	110	80	110
Noise	Sone	0.7	0.6	0.7	0.6	0.7	0.6
Power consumption	Watts	33.3	35.8	28	35	28	35
Energy efficiency	CFM/Watts	2.40	3.08	2.86	3.14	2.86	3.14
Power rating	V/Hz.	120/60	120/60	120/60	120/60	120/60	120/60
Duct diameter	Inches	4" & 6"	4" & 6"	4" & 6"	4" & 6"	4" & 6"	4" & 6"
Weight	lbs	9.9	9.9	9.9	9.9	9.9	9.9
Master Qty.		1	1	1	1	1	1

DELUXE RECESSED SERIES

Recessed Fan Lights

Housing Dimensions

- 12-5/8" L x 8" W x 7-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Adjustable double bar hanger system that extends up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes 4" and 5" metal duct adapter with built-in back draft damper
- Adjustable lamp base holder for flushed lighting mounts
- IC rated up to R40 insulation

Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor
- Quick installation of motor and impeller assembly
- Quiet operation and minimal vibration transfer
- Built-in overload disconnect for safety and longer motor life
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille & Trim

- Durable Polymeric Resin
- Modern and elegant design
- Torsion spring clips included for easy mounting

Warranty

- 2 year limited warranty

Lighting


FANLIGHTS

Not Included:
1 - 16 Watt GU24
Base Compact
Fluorescent Lamp



LED FANLIGHTS

Included:
4.5 Watt LED Lamp,
MR16 trim



OE80RL



OE80RLL

See Fan Curve (3) on Pg.16



TITLE 24
COMPLIANT

		FANLIGHTS		LED FANLIGHTS	
Cat. No.		OE80RL		OE80RLL	
Static pressure	Inches w.g.	0.1"		0.1"	
Air volume	CFM	80		80	
Noise	Sone	1.0		1.0	
Power consumption	Watts	18.8		18.8	
Energy efficiency	CFM/Watts	4.25		4.25	
Power rating	V/Hz.	120/60		120/60	
Duct diameter	Inches	4" & 5"		4" & 5"	
Weight	lbs	9.7		9.7	
Master Qty.		1		1	

DELUXE SERIES

Housing Dimensions

- 9-1/8" L x 9-1/8" W x 7-5/8" H

Housing

- Heavy-duty steel housing coated with rust proof paint
- Adjustable double bar hanger system that extends up to 24"
- 4" exhaust pipe connection
- Wired for both fan or fanlight
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable, and sturdy

Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor with **ball bearings** designed for continuous use
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Contemporary design - with or without light kit
- Durable white ABS for easy cleaning
- Torsion spring clips included for easy mounting
- Electronic ballast

Warranty

- 2 year limited warranty

Lighting

FANLIGHTS

Included:
2 - 18 Watt Flicker-Free,
Electronic Ballast
Compact Fluorescent Lamps



FANLIGHT MODEL

See Fan Curve (4) on Pg.16 or
See Fan Curve (5) on Pg.17



TITLE 24
COMPLIANT

		FANS				FANLIGHTS			
Cat. No.		OD80*	OD90*	OD110*	OD120*	OD80L	OD90L	OD110L	OD120L
Static pressure	Inches w.g.	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"	0.1"
Air volume	CFM	80	90	110	120	80	90	110	120
Noise	Sone	0.8	1.0	1.5	2.0	0.5	0.7	1.2	1.5
Power consumption	Watts	27.9	28.4	30.6	32.1	31.6	32.1	33.7	37.0
Energy efficiency	CFM/Watts	2.87	3.17	3.59	3.74	2.53	2.80	3.26	3.24
Speed	RPM	946	965	1,083	1,153	990	1,017	1,126	1,201
Current	Amps	.18	.18	.19	.2	.27	.26	.27	.30
Power rating	V/Hz.	120/60	120/60	120/60	120/60	120/60	120/60	120/60	120/60
Duct diameter	Inches	4"	4"	4"	4"	4"	4"	4"	4"
Motor type		Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed	Enclosed
Weight	lbs	10	10	10	10	10	10	10	10
Master Qty.		4	4	4	4	4	4	4	4

DELUXE HEAT FAN LIGHT

Housing Dimensions

- 10-1/2" L x 11-3/8" W x 7-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Double hanger bar mounting brackets that are adjustable up to 24"
- Sloped ceiling mounting capability up to 45 degrees
- Includes **detachable 4"** polymeric collar with lightweight built-in back draft damper

Motor

- Power rating of 120V / 60Hz
- Permanently lubricated, energy efficient motor
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet operation
- ETL and cETL listed for tub/shower enclosure when used with a GFCI branch circuit

Heater

- 1000W PTC ceramic heater with metal blower
- Thermal auto-self protection
- Electric shock protection

Grille

- Thermal paint 22 gauge sheet metal
- Torsion spring clips included for easy mounting

Warranty

- 2 year limited warranty


Lighting

FANLIGHTS

Not Included:
2 - 23 Watt GU24
Compact Fluorescent
Lamp



See Fan Curve (6) on Pg.17



TITLE 24
COMPLIANT

Cat. No.		ODHFL110
Static pressure	Inches w.g.	0.1"
Duct diameter	Inches	4" & 6"*
Air volume	CFM	110
Noise	Sone	0.3
Power consumption	Watts	9
Energy efficiency	CFM/Watts	8.9
Power rating	V/Hz.	120/60

*6" polymeric collar available upon request

ECONOMY PLUS SERIES

Housing Dimensions

- 9-1/8" L x 9-1/8" W x 7-5/8" H

Housing

- Heavy-duty steel housing coated with rust proof paint
- Isolation mounting brackets spanning up to 24"
- Includes 4" exhaust pipe connection
- Wired for both fan only or fanlight
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable and sturdy

Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor designed to be continuously active
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Contemporary design - with or without light kit
- Durable white ABS for easy cleaning
- Torsion spring clips included for easy mounting
- Electronic ballast


Warranty

- 2 year limited warranty

Lighting

FANLIGHTS

Included:
2 - 18 Watt Flicker-Free,
Electronic Ballast Compact
Fluorescent Lamps



FANLIGHT MODEL

See Fan Curve (7) & (8)
on Pg.17



TITLE 24
COMPLIANT



		FANS		
Cat. No.		OEP80*	OEP90*	OEP110
Static pressure	Inches w.g.	0.1"	0.1"	0.1"
Air volume	CFM	80	90	110
Noise	Sone	1.3	1.5	2.0
Power consumption	Watts	31.2	24.5	27
Energy efficiency	CFM/Watts	2.56	3.67	4.07
Speed	RPM	1,189	1,227	1,393
Current	Amps	.16	.21	.16
Power rating	V/Hz.	120/60	120/60	120/60
Duct diameter	Inches	4"	4"	4"
Motor type		Enclosed	Enclosed	Enclosed
Weight	lbs	9.2	9.9	9.9
Master Qty.		4	4	4

FANLIGHTS		
OEP80L	OEP90L	OEP110L
0.1"	0.1"	0.1"
80	90	110
1.0	1.1	1.0
29.2	24.5	27.3
2.79	3.67	4.03
1,198	1,251	1,458
.24	.21	.22
120/60	120/60	120/60
4"	4"	4"
Enclosed	Enclosed	Enclosed
9.2	9.9	9.9
4	4	4

ECONOMY SERIES

Housing Dimensions

- **OE50:** 7-3/4" L x 7-3/4" W x 4-1/4" H
- **OE70 & OE80:** 8-1/4" L x 8" W x 4-1/4" H

Housing

- Heavy-duty Galvanized Steel
- Mounting tabs for easy installation
- 4" exhaust pipe connection, except for OE50 is 3"
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration
- Light, durable and sturdy



Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated, energy efficient motor designed to be continuously active
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Contemporary design
- Durable white ABS
- Gloss finish for "quick wipe" cleaning
- Torsion spring clips included for easy mounting

Warranty

- 2 year limited warranty



Cat. No.		OE50	OE70	OE80
Static pressure	Inches w.g.	0.1"	0.1"	0.1"
Air volume	CFM	50	70	80
Noise	Sone	3.0	3.5	4.0
Power consumption	Watts	36.5	27.1	30.8
Energy efficiency	CFM/Watts	1.37	2.58	2.60
Speed	RPM	1,839	1,223	1,334
Current	Amps	.51	.24	.27
Power rating	V/Hz.	120/60	120/60	120/60
Duct diameter	Inches	3"	4"	4"
Motor type		Shaded Pole	Enclosed	Enclosed
Weight	lbs	4.6	6.2	6.2
Master Qty.		12	12	12

STANDARD PLUS SERIES

Housing Dimensions

- **OSP50 & OSP70:** 7-1/2" L x 7-1/4" W x 3-5/8" H
- **OSP70L:** 7-1/2" L x 7-1/4" W x 5-5/8" H

Housing

- Corrosion-Resistant Galvanized Steel
- Built-in mounting ears for ceiling or wall installation
- Torsion mounting
- Wired for both fan only or fanlight
- Includes **detachable 3" or 4"** polymeric collar

Motor and Blower

- Power rating of 120V/60Hz
- Permanently lubricated motor with plug designed for continuous run and easy removal
- Built-in overload disconnect for safety and longer motor life
- Low RPM for quiet performance
- Removable Centrifugal-type Blower Wheel
- ETL and cETL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille

- Contemporary and elegant design
- Durable Polymeric Resin

Warranty

- 2 year limited warranty

Lighting

FANLIGHTS

Included:
1 - 13 Watt GU24
Compact Fluorescent
Lamp



OSP50 & OSP70



OSP70L



Cat. No.		FANS		FANLIGHTS
		OSP50	OSP70	OSP70L
Air volume	CFM	50	70	70
Noise	Sone	3.5	3.5	3.5
Power consumption	Watts	44.3	62.8	62.8
Energy efficiency	CFM/Watts	0.53	1.14	1.14
Power rating	V/Hz.	120/60	120/60	120/60
Duct diameter	Inches	3"	4"	4"
Finish color		White	White	White
Weight	lbs	3.6	3.6	4.6
Master Qty.		12	12	12

*4" polymeric collar available upon request for OSP50

STANDARD SERIES

Housing Dimensions

- 7-5/8" L x 6-3/4" W x 4-1/8" H

Housing

- Galvanized housing resists humid conditions & changing attic temperatures, unlike plain steel housing used in many vents
- Ceiling/wall thickness indicator markings & built-in mounting tabs for quick installation
- Built-in junction box for easy wiring
- Precision balanced, molded fan blade for quiet operation
- Molded duct adaptor with built-in damper



Motor and Heating

- Easy removal and installation of motor assembly with keyhole mounting bracket
- Permanently lubricated motor with plug designed for continuous use
- Units and service parts are CSA listed

Grille

- Attractive molded grille with spring clips for smooth fit against ceiling or wall
- Dishwasher-safe grille with Polycarbonate Light Lens for easy homeowner cleaning

Grille




← 8 1/2" square →

Warranty

- 2 year limited warranty

Housing & Motor



Cat. No.		OS50	OS70
Air volume	CFM	50	70
Noise	Sone	3.2	4.0
Power rating	V/Hz.	120/60	120/60
Duct diameter	Inches	4"	4"
Finish color		White	White
Master Qty.		12	12

STANDARD HEAT FAN LIGHT

Housing Dimensions

- 14" L x 7-3/4" W x 5-3/4" H

Housing

- Galvanized housing resists humid conditions & changing attic temperatures, unlike plain steel housing used in many vents
- Ceiling/wall thickness indicator markings & built-in mounting tabs for quick installation
- Built-in junction box for easy wiring
- Precision balanced, molded fan blade for quiet operation
- Molded duct adaptor with built-in damper
- Combination Lamp Compartment & Aluminum Reflector
- Built-in medium base lampholder included



Motor and Heating

- 950 W fan-forced heating element
- Easy removal and installation of motor assembly with keyhole mounting bracket
- Permanently lubricated motor with plug for quick activations
- Units and service parts are CSA listed

Grille


- Attractive molded grille with spring clips for smooth fit against ceiling or wall
- Dishwasher-safe grille with Polycarbonate Light Lens for easy homeowner cleaning



Warranty

- 2 year limited warranty

Housing & Motor



Cat. No.		OEHL70
Air volume	CFM	70
Noise	Sone	4.0
Duct diameter	Inches	4"
Finish color		White
Master Qty.		4

CONTRACTOR PACKS

Orbit's highly certified and energy efficient ventilation fan and fanlights are available in contractor packs for large projects and quick installations.

- *Easy and secure installation for reduced labor and costs*
- *Universal housing for reduced inventory and greater flexibility*
- *Fitted with the best fan motors in the ventilation market lasting up to 30,000 hours*
- *Optimal energy efficiency-reduces utility costs by up to 50%*
- *No sharp edges to reduce injury in the field*

Ordering Guide Sample






CONTRACTOR PACKS

CONTRACTOR PACKS





STEP 1

Select Housing

Cat.No.		Description	Compatible Models
OE50H		Economy Housing 7-3/4"L x 7-3/4"W x 4-1/4"H 6 Per Carton	OE50
OSPH		Standard Housing 7-1/2"L x 7-1/4"W x 3-5/8"H 6 Per Carton	OSP50
OEPH		Economy Plus Housing 9-1/8"L x 9-1/8"W x 7-5/8"H 4 Per Carton	OEP80 OEP80L OEP90 OEP90L OEP110 OEP110L
ODH		Deluxe Housing 9-1/8"L x 9-1/8"W x 7-5/8"H 4 Per Carton	OD80 OD80L OD90 OD90L OD110 OD110L

STEP 2

Select Grille + Motor

Cat.No.		Air Volume (CFM)	Description	Compatible Models
OE50F		50CFM	Economy 6 Per Carton 1 Grille + 1 Fan Motor	OE50
OSP50F		50CFM	Standard 6 Per Carton 1 Grille + 1 Fan Motor	OSP50
OEP80F OEP90F OEP110F		80CFM 90CFM 110CFM	Economy Plus 4 Per Carton 1 Grille + 1 Fan Motor	OEP80 OEP90 OEP110
OD80F OD90F OD110F		80CFM 90CFM 110CFM	Deluxe 4 Per Carton 1 Grille + 1 Fan Motor	OD80 OD90 OD110

ACCESSORIES 1

Fanlight Conversion Kits

Cat.No.	Grille + light	Description	Compatible Models
OVFM		4 Per Carton 2 - 18W Lamps + Fanlight Grille + Ballast	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L

ACCESSORIES 2

Grille Replacement

Cat.No.		Description	Compatible Models
OEP-G		Economy Plus Grille	OEP80 OEP90 OEP110
OD-G		Deluxe Grille	OD80 OD90 OD110 OD120
ODEP-G		Deluxe & Economy Plus Grille for Fanlights	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L
ODEP-L		Deluxe & Economy Plus Lens	OD80L OEP80L OD90L OEP90L OD110L OEP110L OD120L



WIRING DEVICES

HUMIDITY SENSORS

- Manual On/Off Control
- LED indicator light
- May be used to comply with: ASHRAE, Energy Star, LEED & CALGreen
- 1 year limited warranty
- Stylish decorator design with wall plate included

Cat. No.	Description	Color (Cat. No. - Color Code)		Std. Pkg.
		White	Almond	
FS-100	Fan Switch Electrical Input: 120 volts @ 60Hz Max. Fan Load: 1/8th hp or 3 amps	FS-100-W	FS-100-A	3
FS-200	Fan & Light Switch Electrical Input: 120 volts @ 60Hz Max. Fan Load: 1/8th hp or 3 amps Max. Light Load: 400 watt for a fluorescent light or 500 watt for an incandescent light	FS-200-W	FS-200-A	3

NEW TITLE 24 COMPLIANT



HUMIDITY SENSORS

- RH Range: 20% - 80%
- Differential: 8%RH Max
- Mounting: Wall Mount
- Color: White
- Switch: SPST
- Voltage: 125/250 VAC
- FLA: 7.5Amps @125 VAC, 3.3Amps @ 250 VAC
- Cycle Rating: 50,000 automatic @ 140°F (60°C), 6,000 manual cycles
- Operating temperature: 32°F to 140°F (0°C to 60°C)
- RoHS Compliance
- Approvals: CSA LR 32079

Cat. No.	Description	Std. Pkg.
DS-2080	Wall Mounted Dehumidistat Sensor	25



DS-2080

NEW TITLE 24 COMPLIANT

RESIDENTIAL GRADE DECORATIVE SWITCHES

Features:

- 120~277 VAC
- Rocker-type
- Impact-Resistant Thermoplastic Body
- With Combination Head Screws

Cat. No.	Description	Color (Cat. No. - Color Code)				Std. Pkg.	Master Carton
		White	Ivory	Black	Almond		
2DS15	Double Rocker Switch, 15A, 120~277V Single-Pole Side Wire only	2DS15-W	2DS15-I	2DS15-BK	2DS15-A	10	200
3DS15	Triple Rocker Switch, 15A, 120~277V Single-Pole Push-In Back Wire only, with Ground Pigtail	3DS15-W	3DS15-I	3DS15-BK	3DS15-A	10	200



2DS15



3DS15



FAN ACCESSORIES

FAN ACCESSORIES

45LT-D

Compatible Models

OD80 OEP80
 OD90 OEP90
 OD110 OEP110
 OD120
 OD80L OEP80L
 OD90L OEP90L
 OD110L OEP110L
 OD120L

NEW

Cat. No.	Description	Std. Pkg.
T46	Transition 4" X 6"	1
45LT-D	Ceiling Radiation Fire Damper	1
GUEBA	GU24 to Edison Base adapter	10



T46

45LT-D

GUEBA

REPLACEMENT BULBS

Cat. No.	Description	Std. Pkg.
PL13-GU-27K	13W GU24 Base Compact Fluorescent, 2700K	1
PL23-GU-41K	23W GU24 Base Compact Fluorescent, 4100K	1
R30-GU-41K	Compact Fluorescent Lamp PAR30, GU24 Base, 16W, 4100K	1



PL13-GU-27K



PL23-GU-41K



R30-GU-41K

REPLACEMENT GRILLES

OFLGML

Compatible Models

ODU814H
 OD80H
 OD110H

ORLTML

Compatible Models

OE80RL

NEW

Cat. No.	Description	Std. Pkg.
OFLGML	Fan Light Grille Module with 10W LED Lamp	1
ORLTML	Recess Fan Light Trim Module with 6W MR16 LED Lamp	1




OFLGML




ORLTML


VENTILATION FAN CURVES




See Pg.1 or Pg.2 for Fan Info



See Pg.3 for Fan Info




See Pg.4 for Fan Info




See Pg.5 for Fan Info


VENTILATION FAN CURVES




See Pg.5 for Fan Info



See Pg.6 for Fan Info



See Pg.7 for Fan Info



See Pg.7 for Fan Info

Orbit Product Lines

Your Universal Source for Electrical Products



STEEL PRODUCTS




NEMA ENCLOSURES



WEATHERPROOF PRODUCTS



ELECTRICAL FITTINGS



WIRING DEVICES



EXIT & EMERGENCY LIGHTING



LANDSCAPE LIGHTING



H.I.D. LIGHTING



LED LIGHTING



VENTILATION FANS



CABLES & WIRES



orbit.
Orbit Industries, Inc.

2100 S. Figueroa St.,
Los Angeles, CA 90007
Tel: 1.800.90.ORBIT (67248)
Fax: 213.745.2015

www.orbitelectric.com

Copyright © 2014, Orbit Industries, Inc. All rights reserved.

