DEWALT®





CONTENTS

4V XR	Page 5	METALWORKING & CONCRETE	Page 87
BV XR	Page 15	Grinders, Polishers, Tile Saws, Chop Saws	
D.8V XR	Page 45	DRILLING AND FASTENING Drills & Wrenches	Page 91
ASERS & LASER DISTANCE MEASURES	Page 51	DUST MANAGEMENT	Page 95
AMMERS	Page 59	Extractors & Accessories	
ITRE SAWS & MACHINERY	Page 65	STORAGE ToughSystem, TSTAK & Soft Storage	Page 97
OODWORKING OUTERS Planers Sanders Heatquins Plunge	Page 75 Saws	SERVICES	Page 109

KEY



CHISELLING MODE

Single mode for chiselling only



TWO MODE

For rotary and hammer drilling



THREE MODE
For rotary, hammer drilling and chiselling

Circular Saws, Jigsaws, Reciprocating Saws



IMPACT MECHANISM
Uses rotary impacts to gen Uses rotary impacts to generate extremely high torque



TWO AND THREE SPEED SELECTOR

Many DEWALT tools are available with multiple speeds to offer 123 good control in a variety of applications



Clutch protects the operator against kickback and the tool against overload should the accessory jam



KEYLESS CHUCK



QUICK CHANGE CHUCK Ideal solution to change easily between SDS and 3 jaw



FORWARD AND REVERSE

Forward and reverse action for screwdriving applications



Tool comes complete with 1 battery as standard



2 BATTERIES

Tool comes complete with 2 batteries as standard



3 BATTERIES

Tool comes complete with 3 batteries as standard



Supplied with heavy duty carrying case



VIBRATION CONTROL

AVC Built-in mechanism to reduce the vibration at the hand



Airlock compatible dust extractor port. Allows easy and secure connection to Airlock dust management systems for a cleaner and safer jobsite



Bluetooth' **BLUETOOTH** COMPATIBILITY



Stackable, highly durable, storage solution



TOUGHSYSTEM



CROSS CUT POSITIONING SYSTEM

Projection of LED light along both sides of the blade to form a shadow on the work piece. This provides adjustment free cut line indication for better accuracy and visibility



54V XR FLEXVOLT

Batteries come in a variety of different voltages and capacities



18V XR BATTERIES

Offer capacities for all needs (2Ah to 5Ah)



BRUSHLESS TECHNOLOGY

Helps to increase lifetime of both tool



Batteries come with a 2Ah capacity as standard















DEWALT is a market-leading manufacturer of premium power tools, accessories and anchors and fixings that provides a fully integrated system solution for various applications.

DEWALT tools offer unparalleled performance, with durable construction for a professional finish. Rely on DEWALT to get the job done, with a 3 year guarantee on most tools.





Taking cordless drilling to the next level, the newest DEWALT 54V XR FLEXVOLT range provides true corded performance without the restrictions of the cord. With Brushless motors and Perform & Protect low vibration levels, these tools set the new standard on the jobsite.

With over 100 tools in the range the 18V XR Lithium-lon battery platform is the biggest and fastest growing in our range. All 18V XR products are compatible with XR FLEXVOLT batteries, giving you longer runtime and even greater flexibility meaning the CORDLESS JOBSITE has arrived.



GUARANTEED TOUGH.

Every one of our products are tested at length by genuine construction professionals, ensuring they never let a user down. Under the most demanding jobsite conditions, DEWALT tools earn the right to be labelled Guaranteed Tough® – in the hands of real users.

PERFORM & PROTECT

PERFORM PROTECT

Tools carrying the Perform and Protect shield are designed to exceed the highest demands of the jobsite whilst meeting strict criteria in key health and safety issues:

- CONTROL unique and innovative torque features help to protect the end user from accidental jams
- VIBRATION integrated vibration dampening systems allow users to operate tools safer for longer
- DUST advanced dust control guards against dust inhalation, helping to create a cleaner, safer working environment





54V XR FLEXVOLT 190MM CIRCULAR SAW

Blade Diameter	190 x 30mm
No Load Speed	5800rpm
Max. Depth of Cut (90°)	67mm
Max. Depth of Cut (45°)	49mm
Bevel Capacity	57°
Hand/Arm Vibration	2.5m/s ²



X

X











DCS575N - BARE UNIT

54V XR FLEXVOLT 190MM TRACKED CIRCULAR SAW

\$576T2

Blade Diameter	190 x 30mm
No Load Speed	5800rpm
Max. Depth of Cut (90°)	61mm
Max. Depth of Cut (90°) with Rail	57mm
Max. Depth of Cut (45°)	43mm
Max. Depth of Cut (45°) with Rail	39mm
Bevel Capacity	57°
Hand/Arm Vibration	2.5m/s ²
Track Compatible	Yes













54V XR FLEXVOLT PLUNGE SAW

\$520T2

Blade Diameter	165 x 20mm
No Load Speed	2500 - 4200rpm
Max. Depth of Cut (90°)	59mm
Max. Depth of Cut (90°) with Rail	55mm
Max. Depth of Cut (45°)	44mm
Max. Depth of Cut (45°) with Rail	40mm
Bevel Capacity	47°













<mark>)CS</mark>520NT - BARE UNIT IN TSTAK

54V XR FLEXVOLT RECIPROCATING SAW

No Load Stroke Rate	0 - 3000spm
Stroke Length	28.6mm
Max. Cutting Capacity Timber	300mm
Hand/Arm Vibration - Cutting Boards	12.5m/s ²



X

X



<mark>DCS</mark>388N - BARE UNIT

54V XR FLEXVOLT 216MM MITRE SAW

\$777T2

Blade Diameter	216 x 30mm
No Load Speed	6300rpm
Max. Cutting Capacity (90°/45°)	173 x 62mm
Max. Cutting Capacity (45°/45°)	190 x 48mm
Max. Cutting Capacity (90°/90°)	270 x 62mm
Bevel Capacity	48°
Mitre Capacity	50°/50°











CS777N - BARE UNIT

54V XR FLEXVOLT 250MM MITRE SAW

\$778T2

Blade Diameter	250 x 30mn
No Load Speed	4300rpn
Max. Cutting Capacity (90°/90°)	303 x 110mm & 345 x 76mn
Max. Cutting Capacity (90°/45°)	211 x 112mm & 244 x 76mn
Max. Cutting Capacity (45°/45°)	212 x 76mn
Max. Cutting Capacity (45°/45°)	268 x 63mm & 345 x 44mn
Bevel Capacity	48
Mitre Capacity (Right/Left)	50°/50°









<mark>)CS</mark>778N - BARE UNIT





2 X 54V XR FLEXVOLT 305MM MITRE SAW

Blade Diameter	305 x 30mm
No Load Speed	3800rpm
Max. Cutting Capacity (90°/90°)	303 x 110mm & 345 x 76mm
Max. Cutting Capacity (90°/45°)	211 x 112mm & 244 x 76mm
Max. Cutting Capacity (45°/45°)	212 x 76mm
Max. Cutting Capacity (45°/90°)	268 x 63mm & 345 x 44mm
Mitre Capacity (Right/Left)	60°/50°
Bevel Capacity (Right/Left)	49°/ 49°



X

X

X









DHS780N - BARE UNIT

54V XR FLEXVOLT TABLE SAW

S7485T2

Blade Diameter	210 x 30mm
No Load Speed	5800rpm
Max. Depth of Cut (90°)	65mm
Max. Depth of Cut (45°)	45mm
Bevel Capacity	-3 to 48°
Rip Capacity (Right)	610mm
Rip Capacity (Left)	318mm







<mark>CS</mark>7485N - BARE UNIT

54V XR FLEXVOLT SDS PLUS 3-MODE HAMMER DRILL

H333X2

No Load Speed	0 - 1000rpm
Max. Drilling Capacity Concrete	30mm
Hand/Arm Vibration - drilling into Concrete	7.5m/s ²
Blows Per Minute	0 - 4480bpm
Impact Energy	3.5J

















OCH333NT - BARE UNIT IN TSTAK

54V XR FLEXVOLT SDS PLUS 3-MODE HAMMER DRILL

No Load Speed	0 - 1000rpm
Max. Drilling Capacity Concrete	30mm
Hand/Arm Vibration - drilling into Concrete	7.5m/s
Blows Per Minute	0 - 4480bpm
Impact Energy	3.5.

















X

X

REE

<mark>dch</mark>334n - Bare Unit

54V XR FLEXVOLT SDS MAX 3-MODE HAMMER DRILL

CH481X2

No Load Speed	0 - 540rpr
Max. Drilling Capacity Concrete	40mr
Hand/Arm Vibration - drilling into Concrete	9.4m/s
Blows Per Minute	0 - 3150bpr
Impact Energy	6.1















CH481N - BARE UNIT

54V XR FLEXVOLT ANGLE GRINDER

G414T2

No Load Speed	9000rpm	
Hand/Arm Vibration - Grinding	5.9m/s	
Max. Disc Diameter	125mn	
Spindle Thread	M14	
















54V XR FLEXVOLT ALLIGATOR SAW

CS397T2




Class 20 blade suitable for Poroton and Building Blocks available separately (DT2976-QZ)



DCS397N - BARE UNIT

54V XR FLEXVOLT SPLIT SHAFT STRING TRIMMER

<mark>M</mark>5713X1












54V XR FLEXVOLT TRIMMER & BRUSHCUTTER

<mark>M</mark>571X1

Line Diameter	7.5m x 2.0mm
Cutting Speed	0-5100rpm/0-5600rpm
Cutting Width/Swathe	38cm
Brush Cutter	Yes
Sound Power Level	94dB(A)











54V XR FLEXVOLT BLOWER

M572X1

Blow Speed	0-207km/l
Blow Area Volume	0-423cfn
Variable Speed	Yes
Lock On Switch	Yes
Sound Power Level	99.5dB(A



X



<mark>CM</mark>572N - BARE UNIT

54V XR FLEXVOLT 40CM CHAINSAW

575X1

Bar and Chain Length	40cm
Chain Speed	15m/s
Chain Brake	< 1sec
Variable Speed	Yes
Chain Tensioning	Tool Free
Sound Power Level	100.5dB(A)

Tree Surgeon's License is NOT required to operate this machine





<mark>CM</mark>575N - BARE UNIT

54V XR FLEXVOLT STUD AND JOIST DRILL

D460T2

No Load Speed	0-300 rpm / 0-1,250rpn
Max. Drilling Capacity	152mn
Hand/Arm Vibration - Metal	4.9m/s
Max. Torque	140/130Nn
Power Output	1500V
Chuck Capacity	13mn




















54V XR FLEXVOLT COMPRESSOR

CC1054T2

Tank Size	9.5L
Power	0.3kW/0.4HP
Pump Type	Oil-free
Max. Pressure	9Bar
Free Air Delivery	31 I/min @ 7Bar
Noise LPa 1sd	78.5 dBA
Weight	10kg
18GA Brad Nails per Charge	1220 on 1x 6.0Ah
Regulator Type	OneTurn™
<u> </u>	·





DCC1054N - BARE UNIT

54V XR FLEXVOLT DUAL HANDLE PADDLE MIXER

CD240X2

No Load Speed	225/350/475/600/725rpm
Hand/Arm Vibration	<2.5m/s²
Power Output	2000W
Max. Capacity	160mm
Ramp Up/Down Speed	2.5 secs
Spindle thread	m14
Battery Cover	Yes

Includes Centre Pull Down Swirl Paddle (550 x 200mm)



54V X FLEX 6



DCD240N - BARE UNIT

6.0AH XR FLEXVOLT 18/54V BATTERY PACK

CB546

Voltage	18/54V
Battery	18V 6Ah XR FLEXVOLT
Length	125mm
Width	85mm
Height	90mm





9.0AH XR FLEXVOLT 18/54V BATTERY PACK

X

X

X

Voltage	18/54V
Battery	18V 9Ah XR FLEXVOLT
Length	138mm
Width	87mm
Height	97mm



X

X

X

54V X FLEX 9

XR FAST CHARGER

OCB118

Power Voltage Supply	240V
Battery Compatibility	18/54V
Charging Current	4A/8A
Charging Time (6.0Ah)	60mins





XR DUAL CHARGER

B132

Power Voltage Supply	240V
Battery Compatibility	10.8/14.4/18/54V
Charging Current (Single/Dual)	4A/2 x 4A









CM575N - BARE UNIT



54V XR FLEXVOLT GRINDER AND 18V XR HAMMER DRILL TWIN KIT

OCK2055T2T

Kit Includes:

DCD996 Premium Hammer Drill Driver

DCG414 54V Angle Grinder DCB546 2 x 54V Flexvolt Batteries

DCB118 Fast Charger

N506511 Kitbox

DWST1-17807 (N279261) TSTAK II











DCD240N - BARE UNIT

54V XR FLEXVOLT CIRCULAR SAW AND 18V XR HAMMER DRILL TWIN KIT



CK2056T2T

Kit Includes:

DCD996 Premium Hammer Drill Driver

DCS575 54V Circ Saw

DCB546 2 x 54V Flexvolt Batteries DCB118 Multi-voltage charger

MP16724 (N429655) TSTAK VI

TSTAK compatible and TSTAK VI kit boxes











54V XR FLEXVOLT RECIP SAW AND 18V XR HAMMER DRILL TWIN KIT



CK2057T2T

Kit Includes:

DCD996 Premium Hammer Drill Driver

DCS575 54V Recip Saw

DCB546 2 x 54V Flexvolt Batteries

DCB118 Multi-voltage charger

DWST1-75799 TSTAK compatible and TSTAK II kit boxes















DEWALT


18V XR TOOL

GET CONNECTED. TAKE CONTROL.

Save time and money with Tool Connect. Using the intelligent inventory management platform you will easily maximise your productivity and protect your investment.

Manage and track all your assets with the Bluetooth enabled tag or by connecting the 18V XR battery connector to your existing 18V XR tools. With the new smart 18V tools, you can also customise the tools specifications for the perfect performance.

Take complete control of your own assets, or those of your team, via the Tool Connect App or web platform, and get ready for the jobsite of the future.



18V XR BATTERY

DCB184B



Android Compatible	Yes
iOS Compatible	Yes
Tool Connect Compatible	Yes








18V XR BATTERY

CB183B









18V XR COMPACT HAMMER DRILL DRIVER WITH 2 X 2.0AH BATTERIES

Max. Torque	70Nm
No Load Speed	0 - 550/2000rpm
Beats Per Minute	0 - 9350/34000
Max. Drilling Capacity Wood	40mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	13mm















18V XR XRP 3 SPEED PREMIUM COMBI DRILL

CD997P2B

Max. Torque	95Nm
No Load Speed	0 - 450/1300/2000rpm
No Load Speed (Hammer)	0 - 500/1500/2250
Beats Per Minute	0 - 8600/25500/38250bpm
Max. Drilling Capacity Wood	55mm
Max. Drilling Capacity Metal	15mm
Max. Drilling Capacity Masonry	16mm



















18V XR COMPACT HAMMER DRILL + IMPACT DRIVER + 2 X 5.0AH BATTERIES COMBI DRILL

DCK2500P2B

Kit Includes:

DCD797 Tool Connect Compact Brushless Hammer Drill

DCF888 Tool Connect Brushless Impact Driver DCB184B 2 x 5.0 Ah Tool Connect Batteries

DS150 Toughsystem Kitbox DCB115 240V Charger



18V XR CONNECTOR

18V 5 AH Bluetooth

DCE040











18V XR IMPACT DRIVER 2AH

CF888D2B

Max. Torque	205Nm
No Load Speed	0 - 1000/2800/3250rpm
Impacts Per Minute	0 - 3800ipm
Bit Holder	1/4" (6.35mm)
Max. Bolt Diameter	M12





















18V XR XRP 3 SPEED PREMIUM COMBI DRILL

Max. Torque	95Nm
No Load Speed	0 - 450/1300/2000rpm
No Load Speed (Hammer)	0 - 500/1500/2250rpm
Beats Per Minute	0 - 8600/25500/38250bpm
Max. Drilling Capacity Wood	55mm
Max. Drilling Capacity Metal	15mm
Max. Drilling Capacity Masonry	16mm



18V XR















DCD997P2B-GB - 5AH TOOLCONNECT BLUETOOTH BATTERIES

18V XR XRP 3 SPEED COMBI DRILL

CD985M2

Max. Torque	80Nm
No Load Speed	0 - 575/1350/2000rpm
Beats Per Minute	0 - 9755/22950/34000bpm
Max. Drilling Capacity Wood	50mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	16mm





18V XR 2 SPEED COMPACT COMBI DRILL

796P2

Max. Torque	70Nm
No Load Speed	0 - 550/2000rpm
Beats Per Minute	0 - 9350/34000bpm
Max. Drilling Capacity Wood	40mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	13mm



DCD796D2 - 2AH BATTERIES DCD797D2B - 2AH TOOLCONNECT BLUETOOTH BATTERIES

18V XR XRP 3 SPEED PREMIUM DRILL DRIVER

Max. Torque	95Nn
No Load Speed	0 - 450/1300/2000rpn
No Load Speed (Hammer Mode)	0 - 500/1500/2250rpm
Max. Drilling Capacity Wood	55mn
Max. Drilling Capacity Metal	15mn















18V XR 2 SPEED COMPACT DRILL DRIVER

Max. Torque	70Nn
No Load Speed	0 - 550/2000rpn
Max. Drilling Capacity Wood	40mn
Max. Drilling Capacity Metal	13mn













18V XR 3 SPEED IMPACT DRIVER

F887P2

Max. Torque	205N
No Load Speed	0 - 1000/2800/3250rp
Impacts Per Minute	0 - 3800ip
Bit Holder	1/4" (6.35m
Max. Bolt Diameter	M





















18V XR COMPACT IMPACT WRENCH

Max. Torque	203Nm
No Load Speed	0 - 2300rpm
Impacts Per Minute	0 - 2700ipm
Bit Holder	1/2" (12.7mm)
Max. Bolt Diameter	M16
·	-



18V XR













18V XR 1/2" COMPACT HIGH TORQUE WRENCH

CF894P2

Max. Torque	447Nm
No Load speed	0-900/0-2000rpm
Impacts Per Minute	3100ipm
Hand/Arm Vibration	13.5m/s ²
Power Output	580W
PRECISION WRENCH™	Yes















DCF894N - BARE UNIT

18V XR 3 SPEED HIGH TORQUE IMPACT WRENCH

F899P2

Max. Torque	135/400/950Nm
No Load Speed	0 - 400/1200/1900rpm
Impacts Per Minute	0 - 2400ipm
Bit Holder	1/2" (12.7mm)
Max. Bolt Diameter	M20
Power Output	610W

















<mark>OCF</mark>899N - BARE UNIT <mark>DCF</mark>899HN - BARE UNIT HOG RING

18V XR BRUSHLESS 3/4" HIGH TORQUE IMPACT WRENCH

Max. Torque	950Nm
No Load Speed	0-1900rpm
Impacts Per Minute	0-2400ipm
Bit Holder	3/4" (19.05mm)
Power Output	610W





18V XR COLLATED SCREWDRIVER

CF620P2K

Max. Torque	5 - 30Nm
No Load Speed	0 - 4400rpm
Bit Holder	1/4" (6.35mm)
Power Output	435W













<mark>icf</mark>620D2K - 2ah batteries <mark>dcf</mark>620N - Bare Unit <mark>Dcf</mark>6201 - Collated Mechanism

18V XR SELF DRILLING SCREWDRIVER

F622P2

Max. Torque	34Nn
No Load Speed	0 - 2000rpn
Bit Holder	1/4" (6.35mm
Max. Screw Length	6.15mn
Power Output	850V







23

18V XR

X



18V XR RIGHT ANGLE DRILL

DCD740C1

Max. Torque	33Nm
No Load Speed	0 - 650/2000rpm
Max. Drilling Capacity Wood	28mm
Max. Drilling Capacity Metal	10mm
















18V XR SDS PLUS 3-MODE HAMMER DRILL

CH273P2

No Load Speed	0 - 1100rpm
Blows Per Minute	0 - 4600bpm
Max. Drilling Capacity Concrete	24mm
Impact Energy	2.1J
Hand/Arm Vibration	6.6m/s ²

















OCH274P2 - INCLUDES QUICK CHANGE CHUCK

18V XR SDS PLUS 3-MODE HAMMER DRILL

H253M2

No Load Speed	0 - 1200rpm
Blows Per Minute	0 - 4500bpm
Max. Drilling Capacity Concrete	24mm
Impact Energy	2.1J
Hand/Arm Vibration	6.6m/s ²




















<mark>och</mark>253n - Bare Unit <mark>dch</mark>254m2 - Includes Quick Change Chuck

18V XR 125MM ANGLE GRINDER

CG405P2











18V XR 125MM ANGLE GRINDER

CG412M2

No Load Speed	7000rpm
Max. Disc Diameter	125mm
Spindle Thread	M14
Hand/Arm Vibration	6.0m/s ²





CG412N - BARE UNIT

18V XR BRUSHLESS DIE GRINDER

G426P2

Power Output	760 Wa
No Load Speed	0 - 10000/17500/2500
Max. Disc Diameter	38mr
Collet Size	6mr
Hand/Arm Vibration - Grinding	4.4m/s









DEWALT

18V XR CONCRETE NAILER

DCN890P2

Nail Diameter	2.6 - 3./mm
Magazine Angle	15°
Nail Length	13 - 57mm
Firing Mode	Rapid Cycle™ and Sequential














18V XR CONCRETE NAILER ATTACHMENTS



















18V XR FRAMING NAILER

N692P2

Nail Diameter	2.8 - 3.3mm
Magazine Angle	30 - 34°
Nail Length	50 - 90mm
Firing Mode	Bump & Sequential
Temperature Range	-20 to 50°C











18V XR METAL CONNECTOR NAILER

Nail Diameter	3.4mm
Magazine Angle	33°
Nail Length	35mm
Firing Mode	Rapid Cycle™ and Sequential
Temperature Range	-20 to 50°C












18V XR SECOND FIX NAILER

CN660P2











<mark>dCN</mark>660D2 - Kit with 2AH Batteries <mark>DCN</mark>660N - Bare Unit

18V XR BRAD NAILER

CN680D2


Nail Diameter	1.25mm (18G
Magazine Angle	0° (Straigh
Nail Length	15 - 54m
Firing Mode	Bump & Sequenti
Temperature Range	-20 to 50°















18V XR NARROW CROWN STAPLER

DCN681D2

Nail Diameter	1.25mm (18Ga)
Staple Crown	5.6mm (SX staples)
Magazine Angle	0° (Straight)
Nail Length	12 - 38mm
Firing Mode	Bump & Sequential



18V XR













18V XR FLOORING STAPLER

N682D2

Nail Diameter	1.25mm (18Ga)
Staple Crown	5.6mm (SX staples)
Magazine Angle	0° (Straight)
Nail Length	12 - 38mm
Firing Mode	Rapid Cycle & Sequential
Temperature Range	-20 to 50°C













<mark>)CN</mark>682N - BARE UNIT

18V XR 184MM MITRE SAW

\$365M2

Blade Diameter	184 x 16mm
No Load Speed	3750rpm
Max. Cutting Capacity	250 x 50mm
Bevel Capacity	48°
Mitre Capacity	48 / 48°











DCS365N - BARE UNIT

18 XR BRUSHLESS 184MM CIRCULAR SAW

Blade Diameter	184mn
No Load Speed	5500rpn
Max. Depth of Cut (90°)	64mn
Max. Depth of Cut (45°)	48mn
Bevel Capacity	57
Hand/Arm Vibration	2.5m/s





<mark>DCS</mark>570N - BARE UNIT

18V XR CIRCULAR SAW

DCS391M2

Blade Diameter	165 x 20mm
No Load Speed	5150rpm
Max. Depth of Cut	55mm
Max. Depth of Cut (45°)	42.1mm
Bevel Capacity	50°
Hand/Arm Vibration	<2.5 m/s ²





DCS391N - BARE UNIT

18V XR METAL CUTTING CIRCULAR SAW

<mark>cs</mark>373N

Blade Diameter	140 x 20mm
No Load Speed	3700rpn
Max. Depth of Cut	43mn








18V XR JIGSAW

OCS331M2









18V XR RECIPROCATING SAW

CS380M2

No Load Stroke Rate	0 - 2950spm
Max. Cutting Capacity Wood	300mm
Steel Sections & Pipes	100mm
PVC	100mm
Stroke Length	28.6mm









DCS380N - BARE UNIT

18V XR COMPACT RECIPROCATING SAW

CS367N

No Load Stroke Rate	0 - 2900spm
Max. Cutting Capacity Wood	300mm
Steel Sections & Pipes	100mm
PVC	100mm
Stroke Length	28.6mm





18V XR BANDSAW

S371N

No Load Speed	174 Metre/mir
Max. Cutting Capacity	63mm
Max. Watts Out	460W





18V XR PLANER

CP580P2

No Load Speed	15000rpm
Max. Depth of Cut	2.0mm
Max. Rebating Depth	9.0mm
Planer Width	82mm









DCP580N - BARE UNIT DWV9390 - PLANER DUST BAG

18V XR OSCILLATING TOOL

\$355M2

Oscillations per Minute	0 - 20000opn
Tool Free Accessory Fitment	Ye
Accessories Included	3









<mark>)CS</mark>355D2 - 2AH BATTERIES <mark>DCS</mark>355N - BARE UNIT

X



18V XR DRYWALL CUT OUT TOOL

No Load Speed	26000rpm
Included Collets	3.2mm (1/8")
Max. Watts Out	550W



This product comes without a battery



18V XR THREADED ROD CUTTER

Speed	30spm
Mild Steel	M6, M8, M10, M12
Stainless Steel	M6, M8, M10
Cutters Included	M6, M8, M10, M12





18V XR SHEARS

<mark>:\$</mark>491N

Speed	0 - 2450spm
Mild Steel	1.3mm
Stainless Steel	1.3mm





18V XR CAULK GUN

arrier Size	300 - 600ml
ush Force	2500N
ush Speed	51 - 333mm/min





DCE5601 - 300ML CARTRIDGE ATTACHMENT

18V XR GREASE GUN

GG571M1

Output Pressure	690bar, 10000PS
Feed Rate	147g/mir
Grease Type Up To	NLGI #2
Grease Capacity Bulk	4530
Cartridge	4000







18V XR BRUSHLESS STRING TRIMMER WITH 1 X 5.0AH BATTERY SPLIT SHAFT

M561P1S

Cutting Width/Swathe	33cm
Line Diameter	2mm
Cutting Speed	0 - 4600/0 - 6000rpm





DT20658-QZ SPOOL & 2MM X 8.0M LINE DCM561PBS - BARE UNIT



18V XR BLOWER

DCM562P1



18V XR

Noise Level	<65dE
Blow Speed	144km/t
Variable Speed	Yes
Lock On Switch	Yes



18V DCM562PB - BARE UNIT

18V XR HEDGE TRIMMER



Cutting Gap





DCM563PB - BARE UNIT

18V X 5

18V XR CHAINSAW

M565P1

Bar Length	30cm
Chain Speed	7.68m/s
Chain Brake	< 1sec
Variable Speed	Yes
Chain Tensioning	Tool Free







CM565N - BARE UNIT

18V XR COMPACT BLOWER

Blow Speed	80m
Variable Speed	Υ
Lock On Switch	Υ





XR L-CLASS EXTRACTOR

DCV584L

Battery Compatibility	14.4/18/54V
Max. Airflow	954L/min
Capacity	7.5L
Wet & Dry Filter	Yes





18V XR COMPACT WET & DRY VACUUM

CV517N









DEWALT

18V XR COMPACT RADIO

Battery Compatibility	10.8/14.4/18V
Power Source	AC/D0
Modes	DAB/FM/AUX/USE
USB Charger	5V/2.1A







18V XR RADIO CHARGER

Battery Compatibility	10.8/14.4/18V
Power Source	AC/DC
Modes	DAB/FM/AUX/USB
USB Charger	5V/2.1A









XR RADIO CHARGER

Battery Compatibility	18/54V
Power Source	AC/DC
Modes	DAB+/FM/AUX/USB
USB Charger	5V/2.1A
Output	20W RMS/Channel





18V XR BLUETOOTH SPEAKER

Battery Compatibility	10.8/14.4/18V
AUX Port	3.5mm









BLUETOOTH ADAPTOR

OCR002

Connection Type





18V XR COMPACT LED PIVOT LIGHT

DCL040

Output 110 Lumen













X[°]



18V XR LED SPOT LIGHT

DCL043

Output 120 - 1000 Lumen





18V XR LED PIVOT LIGHT

DCL050

250 - 500 Lumen Output







18V XR LED AREA LIGHT

DCL060

1500 Lumen Output







CL079-XJ

Light output	1000lm, 1800lm, 3000lm
IP Rating	IP55
Max. Runtime	15.6 hours





18V XR 5AH BATTERY

DCB184

Battery Capacity	5.0Al
Tool Connect Compatible	No





18V XR 4AH BATTERY

CB182

Battery Capacity	4.0Al
Tool Connect Compatible	No









18V XR 2AH BATTERY

DCB183







18V XR 12V CAR CHARGER

Battery	Li-lon
Charging Current	2.5A
Charging Time	40-90 min









18V XR 240V CHARGER

OCB115

Battery	XR Li-lon
Charging Current	4.0A
Charging Time	30 (2.0Ah) min

18V 10.8 14.4 18 VOLT VOLT VOLT





18V XR USB CHARGER

Voltage	10.8V, 14.4V, 18V
Battery	Li-lon
Charging Current	1.5A











18V XR COMPACT TWIN KIT

CK266P2

Kit Includes:

DCD796 2 Speed Combi Drill DCF887 Impact Driver DCB184 2 x 5Ah Batteries DCB115 240V Charger 0DS150 Toughsystem Kitbox









DCK266D2 - 2AH BATTERIES

18V XR PREMIUM TWIN KIT

CK276P2

Kit Includes:

DCD996 XRP 3 Speed Combi Drill

DCF887 Impact Driver DCB184 2 x 5Ah Batteries DCB115 240V Charger DS150 Toughsystem Kitbox













18V XR SDS TWIN KIT

OCK229P2T

Kit Includes:

DCD996 XRP 3 Speed Combi Drill DCH273 3 Mode SDS Hammer Drill

DCB184 2 x 5Ah Batteries DCB115 240V Charger DWST1-71195 TSTAK VI Kitbox









18V XR SIX KIT

DCK694P3

Kit Includes:

DCD996 XRP 3 Speed Combi Drill

DCF887 Impact Driver DCS391 Circular Saw DCG412 Grinder DCS331 Jigsaw

DCL040 LED Pivot Light DCB182 3 x 5Ah Batteries DCB115 240V Charger DS300 2 x Toughsystem Kitbox









18V XR SIX KIT

K665P3T

Kit Includes:

DCD796 2 Speed Combi Drill DCS355 Oscillating Tool

DCP580 Planer DWV9390 Planer Bag DCS391 Circular Saw

DCS331 Jigsaw DCL050 LED Pivot Light DCB182 3 x 5Ah Batteries DCB115 240V Charger

DWST1-71195 2 x TSTAK VI Kitbox









18V XR BRUSHLESS COMPACT 6 PIECE KIT

CK623P3

Kit Includes:

DCG405 18V XR 125mm Small Angle Grinder DCS367 18V XR Compact Reciprocating Saw 18V XR 184mm Circular Saw DCS570 DCF887 18V XR 3-Speed Impact Driver 18V XR Compact Hammer Drill Driver DCD796

18V XR Handheld LED Area Light DCL050 1-70-322 x 2 Toughsystem DS300

DCB184 x 3 18V XR 5.0Ah Batteries DCB115 XR Multi-Voltage Charger















X

X

X

DEWALT

10.8V XR COMPACT DRILL DRIVER

DCD710D2

No Load Speed	0 - 400/1500rpm
Max. Torque	24Nm
Max. Drilling Capacity Wood	20mm
Max. Drilling Capacity Metal	10mm

















10.8V XR COMPACT HAMMER DRILL DRIVER

CD716D2

No Load Speed	0-400/1500rpm
Max. Torque	30Nm
Beats Per Minute	0-6000/22500bpm
Max. Drilling Capacity Wood	20mm
Max. Drilling Capacity Metal	10mm
Max. Drilling Capacity Masonry	8mm
















10.8V XR IMPACT DRIVER

F815D2

No Load Speed	0 - 2450rpm
Max. Torque	107Nm
Impacts Per Minute	0 - 3400ipm
Bit Holder	1/4" (6.35mm)
Max. Bolt Diameter	M10





10.8V XR IMPACT WRENCH

No Load Speed	0 - 2450rpm
Max. Torque	130Nm
Impacts Per Minute	0 - 3400ipm
Bit Holder	3/8" (9.525mm) Hog Ring
Max. Bolt Diameter	M12













10.8V XR SCREWDRIVER

CF610D2

No Load Speed	0 - 1050rp
Max. Torque	8Nm
Bit Holder	1/4" (6.35mm)











10.8V XR COMPACT RECIPROCATING SAW

\$310D2

No Load Stroke Rate	0 - 2700spm
Stroke Length	14mm
Hand and Arm Vibration - cutting boards	8.5m/s ²





DEWALT

10.8V XR INSPECTION CAMERA

Cable Size	900 x 17mm
Waterproof Cable	Yes
Wireless Screen	Yes
Zoom	3x
Data Storage	2GB Micro SD Card
Resolution	320 x 480 dpi







10.8V XR INFRARED THERMOMETER

DCT414N

Temperature Range	-29°C to 500°C
Screen Size	36mm
Adjustable Emissivity	0.1 to 1.0
Field of view	30cm x 2.5cm
Data Storage	Micro SD card
LED Indicator	Yes





BARE UNIT

10.8V XR COMPACT TWIN KIT

CK218D2T

Kit Includes:

DCD716 Hammer Drill Driver DCF815 Impact Driver 2 x DCB127 2.0Ah Batteries Multi Voltage Charger DCB113

TSTAK V Kitbox









10.8V XR TWIN KIT

CK211D2T

Kit Includes:

DCD710 Drill Driver DCF815 Impact Driver DCB127 2 x 2Ah Batteries DCB113 Multi Voltage Charger

TSTAK V Clear Lid Organiser









10.8V XR COMPACT LED TORCH

CL510N







BARE UNIT

10.8V XR 2AH BATTERY

CB127


Voltage	10.5
Battery Capacity	2.0















18V XR ROTARY LASER

CE074D1R

Beam Colour	Red
Accuracy	+/-3mm @ 30m
Self-levelling Range	+/-5°
Max. Working Range With De	tector 450m
Sloping Range	+/-10°
IP Rating	54
Tripod Connection	5/8"
Rotation Speed	150, 300, 600, 1200rpm
Laser Class	2
Modes	Vertical, Horizontal, Cross Line, Spot Only Up









18V XR ROTARY LASER

CE079D1G

Beam Colour		Green
Accuracy		+/-1.5mm @ 30m
Self-levelling Range		+/-5°
Max. Working Range W	ith Detector	76-600m
Sloping Range		+/-10°
IP Rating		67
Tripod Connection		5/8"
Rotation Speed		150, 300, 600, 1200rpm
Laser Class		2
Modes	Vertical, Horizo	ntal, Cross Line, Spot Only Up, Down









10.8V XR CROSS LINE LASER

CE088D1G

Beam Colour	Green
Accuracy	+/-3mm @ 10m
Self-levelling Range	+/-4°
Max. Working Range With Detector	or 30-60m
IP Rating	65
Number Of Beams	2 - Horizontal, Vertical
Tripod Connection	5/8", 1/4"
Pendulum Lock	Yes
Laser Class	2
Modes	Vertical Only, Horizontal Only, Cross Line









10.8V XR 3 X 360° CROSS LINE LASER

Beam Colour		Green
Accuracy		+/-3mm @ 10m
Self-levelling Rang	je	+/-4°
Max. Working Rang	ge With Detector	30-60m
IP Rating		65
Number Of Beams		3 - Horizontal, Vertical, Side
Tripod Connection		1/4" x 5/8"
Pendulum Lock		Yes
Laser Class		2
Modes	1 x 360° Horizontal,	1 x 360° Vertical, 2nd 360° Vertical









10.8V XR 5 SPOT CROSS LINE LASER

CE0825D1G

Beam Colour	Green
Accuracy	+/-3mm @ 10m Spot +/-2 @ 10m
Self-levelling Range	+/-4°
Max. Working Range Line/Spot	30m/45m
IP Rating	65
Number Of Beams	7 - Cross Line plus 5 spots
Tripod Connection	1/4" x 5/8"
Pendulum Lock	Yes
Laser Class	2
Modes	Vertical Only, Horizontal Only, Cross Line,
3 Snot Only: Up Down Fron	t 5 Snot Only: Un Down Front Roth Sides









CROSS LINE LASER

N088CG

Beam Colour	Green
Accuracy	+/-3mm @ 10m
Self-levelling Range	+/-4°
Max. Working Range	20-50m
IP Rating	54
Number Of Beams	2 - Horizontal, Vertical
Tripod Connection	1/4"
Laser Class	2
Modes	Vertical Only, Horizontal Only, Cross Line
Power Source	3 x AAA





<mark>)Wo</mark>88K - Red Beam Max. Working range 15-50M with detector <mark>dwo</mark>88kd - includes detector



CROSS LINE LASER

DW089K

Beam Colour	Red
Accuracy	+/-3mm @ 10m
Self-levelling Range	+/-4°
Max. Working Range with Dete	ector 15-50m
IP Rating	54
Number Of Beams	3 - Horizontal, Vertical, Side
Tripod Connection	5/8"
Laser Class	2
Modes Control	3 beams Separately 1 Horizontal, 2 Vertical
Power Source	4AA
	<u> </u>





DW089KD - INCLUDES DETECTOR

RED LINE LASER DETECTOR

DE0892

Compatibility	DW088, DW089
Max. Working Range	50m
Power Source	1 x 9V



GREEN LINE LASER DETECTOR

DE0892G

Compatibility	DW088CG, DCE088D1G, DCE089D1G, DCE0825D1G
Max. Working Range	50m
Power Source	1 x 9V



WATERPROOF DIGITAL ROTARY LASER DETECTOR

DE0772

Compatibility	DCE074D1R
Working Range	Rotary > 300m (Radius)
Power Source	1 x 9V
Adjustable Volume Control	Up to 100dBA



3 SPOT LASER

DW083K

Beam Colour	Red
Accuracy	+/-2mm @ 10m
Self-levelling Range	+/-4°
IP Rating	54
Number Of Beams	3 - Horizontal, 2 Vertical (Up & Down)
Indoor Visibility Range	30m
Tripod Connection	1/4"
Laser Class	2
Power Source	4 x AA





30M LASER DISTANCE MEASURE

DW033

Levelling Accuracy	+/-3mm @ 10n
Max. Working Range	0.15-30n
Laser Class	2
Power Source	2 x AAA





30M BLUETOOTH LASER DISTANCE MEASURE

DW099S

Accuracy	+/-2mm @ 10m
IP Rating	54
Indoor Visibility Range	30m
Power Source	2 x AAA
Calculations	Distance, Area, Volume
Tool Connect Compatible	Yes
App Available	iOS/Android







50M BLUETOOTH LASER DISTANCE MEASURE

DW03050

Accuracy	+/-1.5mm @ 10m
IP Rating	65
Indoor Visibility Range	50m
Power Source	2 x AAA
Calculations	Distance, Area, Volume, Pythagoras
Tool Connect Compatible	Yes
App Available	iOS/Android







100M BLUETOOTH LASER DISTANCE MEASURE

DW03101

Levelling Accuracy	+/-1.5mm @ 10m
IP Rating	65
Indoor Visibility Range	100m
Power Source	2 x AAA
Calculations	Distance, Area, Volume, Pythagoras, Timer Function,
	Inclinometer, Partial Height
Tool Connect Compati	ble Yes
App Available	iOS/Android





-0-00

LASER ACCESSORIES

DE0730

Red Target Card



Aluminium

LASER ACCESSORIES

DE0730G

Green Target Card



LASER ACCESSORIES

DE0881

Mini Tripod

Material

Adjustable Height 0.6 - 1.7m

Mounting Thread 1/4



LASER ACCESSORIES

DE0735

Elevated Laser Tripod

Telescopic Head	Ye
Adjustable Height	1.15 - 3n
Material	Aluminiun
Mounting Thread	11 x 5/8



LASER ACCESSORIES

DE0736

Laser Tripod

Adjustable Height 1.07 - 1.73m

Mounting Threads 11 x 5/8"

Material Aluminium



LASER ACCESSORIES

DE0714G

Glasses For use with green lasers





LASER ACCESSORIES

DE0737

Combi (Cut and fill) Grade Rod

Adjustable Height	2.4m
Spirit Level Bubble Vial	Yes
Sliding Detector Mount	Yes



DE0734 CONSTRUCTION GRADE ROD ALSO AVAILABLE

LASER ACCESSORIES

DE0882

Laser Pole

Adjustable Height	3.4m
Mounting Thread	1/4"



OTHER LEVELS


DW096PK

Auto Level kit

Horizontal Circle Type	Continuous Drive
Accuracy	2mm
Max. Working Range	100m
Magnification	26x
Stadia Ratio	1:100



Kit contains: Auto Level, Tripod, Grade Rod, String Plumb Bob, Carry Case





22MM 3 MODE SDS PLUS HAMMER DRILL

D25033K

Power Input	710W
Max. Drilling Capacity Concrete	22mm
Max. Drilling Capacity Core Bit	50mm
Max. Drilling Capacity Wood	30mm
Max. Drilling Capacity Metal	13mm
Impact Energy	2.0J
No Load Speed	0 - 1550rpm
Blows Per Minute	0 - 5680bpm
Hand/Arm Vibration – drilling into Concrete	13.6m/s ²
Hand/Arm Vibration – Chiselling	12.5m/s ²
Sound Pressure	89dB(A)
Sound Power	100.1dB(A)
Category	2kg





AVAILABLE IN 110V & 240V

26MM 3 MODE SDS PLUS HAMMER DRILL

D25133K

Power Input	800W
Max. Drilling Capacity Concrete	26mm
Max. Drilling Capacity Core Bit	50mm
Max. Drilling Capacity Wood	30mm
Max. Drilling Capacity Metal	13mm
Impact Energy	2.6J
No Load Speed	0 - 1500rpm
Blows Per Minute	0 - 5550bpm
Hand/Arm Vibration – drilling into Concrete	15.4m/s ²
Hand/Arm Vibration – Chiselling	14.9m/s ²
Sound Pressure	89dB(A)
Sound Power	100.1dB(A)
Category	3kg





AVAILABLE IN 110V & 240V

26MM 3 MODE SDS PLUS HAMMER DRILL

D25134K

Power Input	800W
Max. Drilling Capacity Concrete	26mm
Max. Drilling Capacity Core Bit	65mm
Max. Drilling Capacity Wood	30mm
Max. Drilling Capacity Metal	13mm
Impact Energy	2.8J
No Load Speed	0 - 1500rpm
Blows Per Minute	0 - 5540bpm
Hand/Arm Vibration – drilling into Concrete	15.7m/s ²
Hand/Arm Vibration – Chiselling	14.3m/s ²
Sound Pressure	89dB(A)
Sound Power	100.1dB(A)
Category	3kg



AVAILABLE IN 110V & 240V

30MM 3 MODE SDS PLUS HAMMER DRILL

Power Input	950W
Max. Drilling Capacity Core Bit	65mm
Max. Drilling Capacity Wood	30mm
Max. Drilling Capacity Metal	13mm
Impact Energy	3.5J
No Load Speed	0 - 1150rpm
Blows Per Minute	0 - 5200bpm
Hand/Arm Vibration – drilling into Concrete	6.9m/s ²
Hand/Arm Vibration – Chiselling	7.8m/s ²
Sound Pressure	93dB(A)
Sound Power	104dB(A)
Category	4kg











AVAILABLE IN 110V & 240V D25334K - INCLUDES 13MM QUICK CHANGE CHUCK

32MM 3 MODE SDS PLUS MULTI DRILL

D25414KT

1000W
32mm
100mm
32mm
13mm
4.2J
0 - 820rpm
0 - 4700bpm
8.2m/s ²
7.1m/s ²
86dB(A)
97dB(A)
4kg











AVAILABLE IN 110V & 240V

40MM SDS MAX COMBINATION HAMMER

D25481K

Power Input	1050W
Max. Drilling Capacity Concrete	40mm
Max. Drilling Capacity Core Bit	100mm
Max. Drilling Capacity Wood	32mm
Impact Energy	6.1J
No Load Speed	540rpm
Blows Per Minute	3150bpm
Hand/Arm Vibration – drilling into Concrete	9.4m/s ²
Hand/Arm Vibration – Chiselling	7.1m/s ²
Sound Pressure	96dB(A)
Sound Power	107dB(A)
Category	5kg













45MM 3 MODE SDS MAX COMBINATION DRILL

D25601K

Power Input	1250W
Max. Drilling Capacity Concrete	45mm
Max. Drilling Capacity Core Bit	100mm
Impact Energy	8.0J
No Load Speed	0 - 210/415rpm
Blows Per Minute	0 - 1430/2840bpm
Hand/Arm Vibration – drilling into Concrete	8.7m/s ²
Hand/Arm Vibration – Chiselling	7.2m/s ²
Sound Pressure	92dB(A)
Sound Power	103dB(A)
Category	6kg



AVAILABLE IN 110V & 240V

5KG SDS MAX DEDICATED CHIPPING HAMMER

D25810K

Power Input	1050W
Impact Energy	7.1J
Blows Per Minute	3150bpm
Hand/Arm Vibration – Chiselling	8.5m/s ²
Sound Pressure	94dB(A)
Sound Power	105dB(A)
Category	5kg









AVAILABLE IN 110V & 240V

10KG SDS MAX DEMOLITION HAMMER

D25899K

Power Input	1500W
Impact Energy	17.9J
Blows Per Minute	2040bpm
Hand/Arm Vibration – chiselling into Concrete	12.0m/s ²
Sound Pressure	86dB(A)
Sound Power	100dB(A)
Category	10kg





AVAILABLE IN 110V & 240V

10KG SDS MAX DEMOLITION HAMMER

D25902K

Power Input	1550W
Impact Energy	19.0
Blows Per Minute	1050/2100bpm
Hand/Arm Vibration – chiselling into Concrete	7.5m/s
Sound Pressure	89dB(A
Sound Power	100dB(A
Category	10kg





AVAILABLE IN 110V & 240V

30KG PAVEMENT BREAKER

D25981

Power Input	2100W
Impact Energy	62J
Blows Per Minute	960bpm
Hand/Arm Vibration	4.8m/s ²
Tool Holder	28mm HEX
Sound Pressure	94dB(A)
Sound Power	105dB(A)
Category	30kg





ONLY AVAILABLE IN 110V D259811 - TROLLEY FOR D25981

SDS PLUS EXTRACTION TELESCOPE

D25301D

Compatible With

All DEWALT SDS-Plus hammers with a 43mm or 54mm collar diameter

Max. Drill Bit Diameter	16mm
Max. Drill Bit Length	224mm
Max. Drill Bit Depth	150mm
Hose Diameter	35mm



63



INTEGRATED SDS PLUS DUST EXTRACTOR

D25304DH

Compatible With DCH333, DCH334, D25334

Max. Drill Bit Diameter	26mn
Max. Drill Bit Length	250mn
Max. Drill Bit Depth	180mm
Washable HEPA filter	99.5% efficiency for dust particles (-0.3 microns



INTEGRATED HAMMER DRILL DUST EXTRACTOR

D25303DH

Compatible with DCH273

Collar Bit Diameter	54mm
Max. Drill Bit Diameter	16mm
Max. Drill Bit Length	120mm
Max. Drill Bit Depth	105mm
Washable HEPA filter	99.5% efficiency for dust particles (-0.3 microns)





DEWALT

MIRE SAW RANGE

















18V 184MM **DCS**365

- MAX CAPACITY 250 x 50mm
- WEIGHT 10.5Kg • Available with 2 x 4.0Ah batteries (M2) and bare unit (N)

216MM DWS774

- MAX CAPACITY 250 x 62mm
- WEIGHT 12Kg POWER 1400 WATT

216MM

- **DWS**777
- MAX CAPACITY 250 x 62mm
- WEIGHT 14Kg
- POWER 1800 WATT

XFLEX

54V 216MM **ICS**777

- MAX CAPACITY 270 x 62mm
- WEIGHT 14Kg
- Available with 2 x 6.0Ah batteries (T2) and bare unit (N)

250MM **DWS778**

- MAX CAPACITY 305 x 85mm
- WEIGHT 17.2Kg
- POWER 1850 WATT

54V 250MM **DCS**778

- MAX CAPACITY 305 x 85mm
- WEIGHT 17.2Kg Available with 2 x 6.0Ah batteries (T2) and bare unit (N)

250MM DW717XPS

- MAX CAPACITY 301 x 58mm / 320 x 76mm
- WEIGHT 23Kg
- POWER 1675 WATT

2 X 54V 305MM **DWS780**

- MAX CAPACITY 303 x 110mm
- WEIGHT 24.8Kg
- POWER 1675 WATT

2 X 54V 305MM **DHS780**

- MAX CAPACITY 303 x 110mm
- WEIGHT 25.5Kg
- Available with 2 x 6.0Ah batteries (T2) and bare unit (N)

FIRST FIX

SECOND FIX



216MM MITRE SAW



DWS774

Blade Diameter	216 x 30mm
Power Input	1400W
No Load Speed	4500rpm
Max. Cutting Capacity Width x Height	250 x 62mm
Mitre Capacity	48 / 48°
Bevel Capacity	48°





AVAILABLE IN 110V & 240V

216MM MITRE SAW



DWS777

Blade Diameter	216 x 30mm
Power Input	1800W
No Load Speed	6300rpm
Max. Cutting Capacity Width x Height	270 x 62mm
Mitre Capacity	50 / 50°
Bevel Capacity	48°





AVAILABLE IN 110V AND 240V – 110V IS 1600W

250MM MITRE SAW



DWS778

Blade Diameter	250 x 30mm
Power Input	1850W
No Load Speed	4300rpm
Max. Cutting Capacity Width x Height	305 x 85mm
Mitre Capacity	50 / 50°
Bevel Capacity	48°





AVAILABLE IN 110V AND 240V – 110V IS 1650W

250MM MITRE SAW

XPS CROSS CUT POSITIONING SYSTEM

DW717XPS

Blade Diameter	250 x 30mm
Power Input	1675W
No Load Speed	4000rpm
Max. Cutting Capacity Width x Height	302 x 88mm
Mitre Capacity	50 / 60°
Bevel Capacity	48 / 48°





AVAILABLE IN 110V AND 240V – 110V IS 1650W

250MM MITRE SAW



DWS780

Blade Diameter	305 x 30mm
Power Input	1675W
No Load Speed	4000rpm
Max. Cutting Capacity Width x Height	303 x 110mm
Mitre Capacity	60 / 50°
Bevel Capacity	49 / 49°





AVAILABLE IN 110V AND 240V - 110V IS 1650W





MITRE SAW ATTACHMENTS

Universal Leg Stand	DE7023
Short Beam Universal Leg Stand	DE7033
Heavy Duty Saw Horse	DE7035
Work Support Stop	DE7024
Mounting Bracket	DE7025
Roller Support For DE7023	DE7027
Extension Arm Support For DE7023	DE7028
Increased Width Support Stop For DE7023	DE7029
Large Mitre Bracket For DE7023	DE7030
Extension Support For DE7023	DE7031
Mitre Saw Rolling Stand	DE7260

FLIP OVER SAW ATTACHMENTS

Pair Of Push Sticks	DE3454
Length Stop For Short Work Pieces	DE3460
Clamp Assembly	DE3461
Swivel Stop	DE3462
Single Sliding Table	DE3471
Right Side Extension Table	DE3472
Ripping / Parallel Fence	DE3473
Adjustable Support	DE3474
Pair Of Guide Rods 500mm	DE3491
Pair Of Guide Rods 1000mm	DE3494
Material Support Plate	DE3495
Fence For Bench Mode	DE3496

250MM FLIP OVER SAW

DW743N

Blade Diameter	250 x 30mm
Power Input	2000W
No Load Speed	2850rpm
Max. Cutting Capacity Width x Height Mitre	140 x 68mm
Max. Depth of Cut (Sawbench Position)	70mm, 180(w), 70(d)
Mitre Capacity	45 / 45°
Bevel Capacity	45°



DW 743M

250MM HEAVY DUTY LIGHTWEIGHT TABLE SAW

DW745

Blade Diameter	250 x 30mm
Power Input	1850W
No Load Speed	3800rpm
Max. Depth of Cut (90°)	77mm
Max. Depth of Cut (45°)	57mm
Max. Ripping Capacity Right/Left	610/315mm
Bevel Capacity	-3 to 48°



AVAILABLE IN 110V AND 240V – 110V IS 1850W

250MM TABLE SAW

DWE7491

Blade Diameter	250 x 30mm
Power Input	2000W
No Load Speed	3800rpm
Max. Depth of Cut (90°)	77mm
Max. Ripping Capacity Right/Left	558/825mm
Bevel Capacity	-3 to 48°



AVAILABLE IN 110V* & 240V (*EQUAL TO 1500W)

TABLE SAW LEG STANDS

Table Saw Rolling Stand	DE7400
Rolling Leg Stand for Table Saws	DWE74911
Scissor Leg Stand for Table Saws	DWE74912
Scissor Leg Stand for DW745	DW745-DE7450





AVAILABLE IN 110V AND 240V – 110V IS 1550W



PORTABLE THICKNESSER

DW733

Power Input	1800W
No Load Speed	10000rpm
Max. Capacity	317mm
Max. Thicknesser Capacity	152mm
Max. Planing Depth	2mm
Feed Rate	8m/min



AVAILABLE IN 240V

PLANER THICKNESSER

D27300

Power Input	2100W
No Load Speed	6200rpm
Max. Capacity	260mm
Max. Thicknesser Capacity	160mm
Max. Planing Depth	3mm
Feed Rate	5m/min



AVAILABLE IN 240V

BANDSAW

DW876

Power Input	1000W
Max. Cutting Height	200mm
Max. Cutting Width	310mm
Cutting Speed	380/880m/min



AVAILABLE IN 240V

300MM RADIAL ARM SAW

DW721KN

Power Input	2000W
Blade Diameter	300 x 30mm
No Load Speed	3000rpm
Max. Cutting Capacity Width x Height	507 x 90mm
Max. Cutting Speed	36m/sec



AVAILABLE IN 240V

350MM RADIAL ARM SAW

DW729KN

Blade Diameter	350 x 30mm
Power Input	4000W
No Load Speed	2780rpm
Max. Cutting Capacity Width x Height	525 x 110mm
Max. Cutting Speed	53m/sec




FULL METAL SAWHORSE - TWIN PACK

DWST1-75676

Width	135mm
Height	1117mm
Depth	120mm
Capacity	900kg









OSCILLATING TOOL

DWE315KT

Power Input	300W
No Load Speed	0-22000opm
Accessory Change	Quick Release
Accessories Included	37





AVAILABLE IN 110V & 240V

165MM CIRCULAR SAW

DWE550

Blade Diameter	165 x 20mm
Power Input	1200W
No Load Speed	5500rpm
Max. Depth of Cut (90°)	55mm
Max. Depth of Cut (45°)	35mm
Bevel Capacity	48°





AVAILABLE IN 110V & 240V

184MM CIRCULAR SAW

DWF560

Blade Diameter	184 x 16mm
Power Input	1350W
No Load Speed	5500rpm
Max. Depth of Cut (90°)	65mm
Max. Depth of Cut (45°)	42mm
Bevel Capacity	48°





DWE560K - INCLUDES KITBOX AVAILABLE IN 110V & 240V

190MM CIRCULAR SAW

DWE575K

Blade Diameter	190 x 30mm
Power Input	1600W
No Load Speed	5200rpm
Max. Depth of Cut (90°)	67mm
Max. Depth of Cut (45°)	49mm
Bevel Capacity	57°





AIR LOCK

AVAILABLE IN 110V & 240V

190MM CIRCULAR SAW RAIL COMPATIBLE

DWE576K

Blade Diameter	190 x 30mm
Power Input	1600W
No Load Speed	5200rpm
Max. Depth of Cut (90°) with Rail	61mm
Max. Depth of Cut (45°) with Rail	43mm
Bevel Capacity	57°







AVAILABLE IN 110V & 240V

235MM CIRCULAR SAW

D23700

Blade Diameter	235 x 30mm
Power Input	1750W
No Load Speed	4700rpm
Max. Depth of Cut (90°)	86mn
Max. Depth of Cut (45°)	62mm
Bevel Capacity	45°
No Load Speed Max. Depth of Cut (90°) Max. Depth of Cut (45°)	4700r 86r 62r



AVAILABLE IN 110V & 240V



PLUNGE SAW

DWS520K

Power Input	1300W
Blade Diameter	165 x 20mm
No Load Speed	1750 - 4000rpm
Max. Depth of Cut (90°) with Rail	55mm
Max. Depth of Cut (45°) with Rail	44mm
Bevel Capacity	47°





AVAILABLE IN 110V & 240V

PLUNGE SAW ATTACHMENTS



JIGSAW

DW331K

Power Input	701W
No Load Stroke Rate	0 - 3100spm
Max. Depth of Cut Wood	130mm
Max. Depth of Cut Steel	12mm
Bevel Capacity	45°
Stroke Length	26mm
Max. Depth of Cut (Non Ferrous Metal)	30mm





AVAILABLE IN 110V & 240V

COMPACT JIGSAW

DW341K

Power Input	550W
No Load Stroke Rate	0 - 3100spm
Max. Depth of Cut Wood	85mm
Max. Depth of Cut Steel	10mm
Bevel Capacity	45°
Stroke Length	20mm
Max. Depth of Cut (Non Ferrous Metal)	20mm





AVAILABLE IN 110V & 240V

RECIPROCATING SAW

DWE305PK

Po	wer Input	1100W
No	Load Stroke Rate	0 - 2800spm
Ma	ax. Cutting Capacity Cutting Wood	280mm
Ma	ax. Cutting Capacity Steel Section & Pipes	100mm
Ma	ax. Cutting Capacity PVC	130mm
На	nd/Arm Vibration - cutting Wood	19.5m/s ²
St	roke Length	29mm
_		





AVAILABLE IN 110V & 240V



COMPACT RECIPROCATING SAW

DWE357K

Power Input	1050W
No Load Stroke Rate	0 - 2800spm
Max. Cutting Capacity Wood	280mm
Max. Cutting Capacity Steel Sections & Pipes	100mm
Max. Cutting Capacity PVC	130mm
Stroke Length	29mm
Hand/Arm Vibration - cutting Wood	29m/s ²





AVAILABLE IN 110V & 240V

HEAVY DUTY RECIPROCATING SAW

DW311K

Power Input	1200W
No Load Stroke Rate	0 - 2600spm
Max. Cutting Capacity Cutting Wood	300mm
Max. Cutting Capacity Steel Sections & Pipes	130mm
Max. Cutting Capacity PVC	160mm
Stroke Length	28mm
Hand/Arm Vibration - cutting Wood	23.3m/s ²





AVAILABLE IN 110V & 240V

430MM ALLIGATOR SAW

DWE397

Power Input	1700W
No Load Stroke Rate	3000spm
Stroke Length	40mm
Blade Length	430mm
Blade Stop	0.2sec
Blade	TCT Class 12



DT2976-QZ 430mm Class 20 blade suitable for Poroton and Building Blocks available separately.

AVAILABLE IN 110V & 240V

2.5MM PLANER

DW680K

Power Input	600W
No Load Speed	15000rpm
Max. Depth of Cut	2.5mm
Max. Rebating Depth	12mm
Planer Width	82mm
Shoe Length	290mm
Drum Diameter	54mm





AVAILABLE IN 110V & 240V

4MM PLANER

D26500K

Power Input	1050W
No Load Speed	13500rpm
Max. Depth of Cut	4mm
Max. Rebating Depth	25mm
Planer Width	82mm
Shoe Length	320mm
Drum Diameter	64mm





DE2650 - DUSTBAG FOR D26500K

LAMINATE TRIMMER

DWE600!

Power Input	590W
No Load Speed	16000 - 34000rpm
Plunge	25.4mm
Collet Size	1/4"
Max. Cutter Diameter	29mm



AVAILABLE IN 110V & 240V



1/4" FIXED BASE ROUTER

126200

Power Input	900W
No Load Speed	16000 - 27000rpm
Max. Cutter Diameter	30mm
Plunge	55mm
Collet Size	1/4"



AVAILABLE IN 110V & 240V

1/4" ROUTER

DW615

Power Input	1000W
No Load Speed	8000 - 24000rpm
Max. Cutter Diameter	30mm
Plunge	35mm
Collet Size	1/4"



AVAILABLE IN 110V & 240V

1/4" ROUTER

D26203

Power Input	900W
No Load Speed	16000 - 27000rpm
Max. Cutter Diameter	30mm
Plunge	55mm
Collet Size	1/4"



AVAILABLE IN 110V & 240V

1/4" TWIN BASE ROUTER

D26204K

Power Input	900W
No Load Speed	16000 - 27000rpm
Max. Cutter Diameter	55mm
Plunge	55mm
Collet Size	1/4'





AVAILABLE IN 110V & 240V

1/2" ROUTER

DW625EK

Power Input	2000V
No Load Speed	8000 - 20000rpn
Max. Cutter Diameter	50mn
Plunge	80mn
Collet Size	1/2





AVAILABLE IN 110V & 240V

BISCUIT JOINTER

DW682K

Power Input	600\
No Load Speed	10000rpr
Max. Cutter Diameter	100mr
Max. Cutting Depth	20mr
Fence Adjustment	0 - 90





AVAILABLE IN 110V & 240V



DETAIL SANDER

D26430

Power Input	300W
Orbits Per Minute	28000 - 44000opm
Orbit Size	1.8mm
Paper Size	93 x 93 x 93mm
Rotation Speed	14000 - 22000rpm



AVAILABLE IN 240V

1/4 SHEET PALM SANDER

DWE6411

Power Input	230W
Orbit Size	1.6mm
Paper Size	140 x 9115mm





AVAILABLE IN 110V & 240V

125MM RANDOM ORBIT SANDER

DWE6423

Power Input	280W
Orbits Per Minute	8000 - 12000opm
Orbit Size	2.6mm
Paper Size	140 x 115mm





AVAILABLE IN 110V & 240V

150MM RANDOM ORBIT SANDER

D26410

Power Input	400W
Orbits Per Minute	8000 - 20000opm
Orbit Size	3.0/6.0mm
Paper Size	150mm
Rotation Speed	4000 - 10000rpm



AVAILABLE IN 110V & 240V

1/2 SHEET SANDER

D26421

Power Input	350W
Orbits Per Minute	22000opm
Orbit Size	2.5mm
Paper Size	113 x 280mm
Rotation Speed	44000rpm



AVAILABLE IN 110V & 240V

BELT SANDER

DWP352VS

Power Input	1010V
Belt Speed	270 - 440m/mir
Belt Size	75 x 533mn



AVAILABLE IN 110V & 240V



HEATGUN

D26411

Power Input	1800V
Operating Temperature	50 - 600°C
Air Flow	250 / 450l/mir
LCD Screen	No



AVAILABLE IN 240V

DIGITAL HEATGUN

D26414

Power Input	2000W
Operating Temperature	50 - 600°C
Air Flow	650l/min
LCD Screen	Yes



AVAILABLE IN 110V & 240V







115MM ANGLE GRINDER

DWE4206

Power Input	1010W
No Load Speed	11000rpm
Max. Disc Diameter	230mm
Vibration	8.3m/s ²



DWE4206K - INCLUDES KITBOX AVAILABLE IN 110V & 240V

230MM ANGLE GRINDER

DWE490

Power Input	2000W
No Load Speed	6600rpm
Max. Disc Diameter	230mm
Vibration	7.1m/s ²



AVAILABLE IN 240V

115MM/125MM SURFACING SHROUD

DWE46150

Fits all DEWALT 115mm & 125mm Grinders with keyless clamp



230MM ANGLE GRINDER

DWE492K

Power Input	2200W
No Load Speed	6600rpm
Max. Disc Diameter	230mm
Vibration	7.1m/s





AVAILABLE IN 110V & 240V

MORTAR RAKING KIT

DWE46105

Power Input	1400W
No Load Speed	9300rpm
Max. Disc Diameter	125mm
Vibration	9.4m/s ²



AVAILABLE IN 110V & 240V

POLISHER

DWP849X

Power Input	1250V
No Load Speed	0 - 600/3500rpn
Max. Disc Diameter	230mn
Vibration	2.3m/s



AVAILABLE IN 240V



ABRASIVE CHOP SAW

D28710

Power Input	2200W
No Load Speed	3800rpm
Disc Diameter	355mm
Vibration	3.3m/s ²
Max. Cutting Capacity Square Profile	120 x 120mm



AVAILABLE IN 110V & 240V

TCT CHOP SAW

DW872

Power Input	2200W
No Load Speed	1300rpm
Disc Diameter	355mm
Max. Cutting Capacity Square Profile	100 x 100mm



AVAILABLE IN 110V & 240V

TILE SAW


D24000

Power Input	1600W
No Load Speed	4200rpm
Disc Diameter	250mm
Vibration	<2.5m/s ²
Max. Cutting Capacity	610mm
Max. Depth of Cut	95mm



D240001 Leg Stand also available.

AVAILABLE IN 110V & 240V





RIGHT ANGLE DRILL

D21160

Power Input	350W
No Load Speed	0 - 1200rpm
Max. Drilling Capacity Wood	20mm



AVAILABLE IN 240V

PERCUSSION DRILL

DWD024K

Power Input	701W
No Load Speed	0 - 2800rpm
Max. Drilling Capacity Wood	25mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	16mm
Max. Torque	8.6Nm
Blows Per Minute	0 - 47600bpm







AVAILABLE IN 110V & 240V

PERCUSSION DRILL

WD524KS

Power Input	1100W
No Load Speed	0 - 1250/3500rpm
Max. Drilling Capacity Wood	40mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	22mm
Max. Torque	40Nm
Blows Per Minute	0 - 56000bpm













DIAMOND DRILL

D21570K

Power Input	1300W
No Load Speed	0 - 1250/3500rpm
Max. Drilling Capacity Masonry	127mm









AVAILABLE IN 110V & 240V

DIAMOND DRILL

D21580K

Power Input	1705W
No Load Speed	0 - 1110/2350rpm
Max. Drilling Capacity Masonry	152mm







AVAILABLE IN 110V & 240V

IMPACT WRENCH

DW292

Power Input	710V
No Load Speed	0 - 2200rpn
Max. Torque	440Nn
Impacts Per Minute	2700ipm
Tool Holder	1/2
Max. Bolt Diameter	M20







AVAILABLE IN 110V & 240V



IMPACT WRENCH

DW294


Power Input	710W
No Load Speed	0 - 2200rpm
Max. Torque	440Nm
Impacts Per Minute	2700ipm
Tool Holder	3/4'
Max. Bolt Diameter	M20







AVAILABLE IN 110V







L-CLASS DUST EXTRACTOR

DWV901L



M-CLASS DUST EXTRACTOR

WV902M

Power Input	1400W
Max Airflow	4080I/min
Capacity	381
Power Take Off Rating*	2200W
Wet/Dry	Yes



AVAILABLE IN 110V & 240V

AVAILABLE IN 110V & 240V

*@ 240V

DUST EXTRACTOR ACCESSORIES

Replacement Filter for DWV900, DWV901 and DWV902	DWV9340
Disposable Plastic Liner for DWV902M (Pack of 5)	DWV9400
Paper Bag for DWV902M (Pack of 5)	DWV9401
Fleece Bag for DWV902M (Pack of 5)	DWV9402
TSTAK Vac Rack Attachment	DWV9500
Safety Specs	D500910









AIRLOCK ATTACHMENTS

DWV9110
DWV9120
DWV9130
DWV9150
DWV9210
DWV9220
DWV9350
D279058CL





Site Tough Flexible Storage System ToughSystem



Unbeatable toughness, performance and protection:

- 4mm thick reinforced polypropylene plastic
- Heavy duty metal latches and metal hinges
- Dust tight and water jet resistant (IP65) to withstand the most severe weather conditions

A Mobile & Modular **Storage System TSTAK**



Stack boxes in a variety of configurations:

- Strong, easy to use interlocking system
- Can be configured to your exact requirements
- Features such as metal latches and ball bearing slides provide reliability

Heavy Duty Bags and Pouches **Soft Storage**



Lightweight, convenient solutions that will stand up to everyday use in a heavy construction environment:

- Pockets compatible with DEWALT Organiser Cups
- 1200 Denier strong and durable polyester fabric
- Rugged PVC Bottom cover waterproof & protects from wear
- Double reinforced front pockets



TSTAK RADIO

DWST1-81079

Width	465mm
Height	380mm
Depth	165mm
IP Rating	54
Battery Platform	10.8V/18V/54V XR batteries
Speakers	6 inc. 2 sub woofers
Screen	Colour
Output	45W





Bluetooth, DAB+, FM, AM, 3.5mm AUX and Fast Charge USB

TOUGHSYSTEM RADIO

DWST1-75663

Width	545mm
Height	155mm
Depth	360mm
IP Rating	54
Charges	14.4/18V XR batteries
Speakers	6 inc. 2 sub woofers
Screen	Orange & Black
Output	40W





Bluetooth, DAB+, FM, AM, 3.5mm AUX and USB Rubber overmold for the toughest jobsites

TOUGHSYSTEM ORGANISER

DWST1-75522

Width	543mm
Height	100mm
Depth	350mm
IP Rating	65





TOUGHSYSTEM DS150

1-70-321

Width	550mm
Height	158mm
Depth	336mm
IP Rating	65
Weight Capacity	30kg





TOUGHSYSTEM DS280

DWST1-75654

Width	558mm
Height	277mm
Depth	330mm
Weight Capacity	20kg





TOUGHSYSTEM DS300

1-70-322

Width	550mm
Height	306mm
Depth	366mm
IP Rating	65
Weight Capacity	50kg







TOUGHSYSTEM DS400

Width	550mm
Height	408mm
Depth	366mm
IP Rating	65
Weight Capacity	50kg





TOUGHSYSTEM DS450

DWST1-75668

Width	480mm
Height	597mm
Depth	99mm
IP Rating	65
Weight Capacity (Box)	40kg
Weight Capacity (used as trolley)	70kg





TOUGHSYSTEM KIT

DS150	1-70-321
DS300	1-70-322
DS400	1-70-323
Trolley	1-70-324
IP Rating	65
Width	508mm
Height	1092mm
Depth	660mm
Weight Capacity (used as trolley)	120kg





TOUGHSYSTEM DS290 2 DRAWER

DWST1-80123

Width	554mm
Height	340mm





TOUGHSYSTEM DS295 3 DRAWER

DWST1-81055

Width	554mm
Height	340mm
Depth	307mm





TOUGHSYSTEM DS404 COOLER BOX

DWST1-81333

55.2cm
36.8cm
48.3cm
65
Commercial grade
Up to 5 days
50Kg/25.5L





DEWALT

TOUGHSYSTEM ACCESSORIES

DWST1-75694

Trolley	1-70-324
Spare Brackets	1-70-362
Foam Insert For DS150	DWST7-97150









DWST1-75694

TSTAK I

TOUGHSYSTEM"

DWST1-70704

Width	40mm
Height	331mm
Depth	185mm
Weight Capacity	30kg





TSTAK II

DWST1-70703

Width	440mm
Height	331mm
Depth	176mm
Weight Capacity	30kg





TSTAK III

DWST1-70705

Width	440mm
Height	314mm
Depth	176mm
Drawer	Yes
Cups	Yes
Weight Capacity	30kg





TSTAK IV

DWST1-70706

Width	440mm
Height	314mm
Depth	176mm
Weight Capacity	7.5kg





TSTAK V

DWST1-71194

Width	440mm
Height	145mm
Depth	332mm
Weight Capacity	20kg







TSTAK VI

DWST1-71195

Width	440mm
Height	301mm
Depth	332mm
Weight Capacity	30kg





TSTAK COMBO

DWST1-70702

Width	440mm
Height	331mm
Depth	326mm
TSTAK II	DWST1-70703
TSTAK IV	DWST1-70706





TSTAK TOTE

DWST1-71228

TSTAK*

Width	440mm
Height	275mm
Depth	320mm
Weight Capacity	10kg



TSTAK RADIO

DWST1-81079-GB

Width	490mm
Height	700mm
Depth	205mm



TSTAK DEEP

DWST1-75774

Width	442mm
Height	380mm
Depth	323mm
Weight Capacity	30kg





TSTAK MOBILE STORAGE

DWST1-75799

435mm
1000mm
512mm







TSTAK CART

DWST1-71229

Width	486mm
Height	181mm
Depth	436mm
Weight Capacity	100kg





TSTAK™



TSTAK ACCESSORIES

DWST1-71196

Width	490mm
Height	700mm
Length	285mm
Weight Capacity	100kg



TSTAK ACCESSORIES

DWST1-72364

TSTAK

Width	300mn
Length	430mn
TSTAK Foam Inlay	DWST1-7236



DWST1-81042/DWST1-81045

Width	1040mm
Depth	100mm
Height (Standard/High)	1633mm/2143mm
Brackets (Standard/High)	3/4
Max. Load	70kg

VAN RACKING SYSTEM - STANDARD/HIGH

Crash Tested Loading:

Crash-tested telescopic metal bars allow height adjustment to fit all types of vans. Reinforced brackets allow 20kg capacity per pair and fold in when not in use to allow for maximum space efficiency. Brackets fit all ToughSystem modules.



No TOUGHSYSTEM boxes are included



WORKSHOP RACKING

DWST1-75694

Toughsystem

Height	1800mm
Width	650mm
Depth	330mm
Max Load	200kg





No TOUGHSYSTEM boxes are included

TOTE BAG

1-79-208

Width	338mm
Height	323mm
Depth	380mm
Weight Capacity	25kg
100 to 2 to	



RIGID OPEN MOUTH BAG

1-79-20

Width	500mm
Height	310mm
Depth	300mm
Weight Capacity	25kg



ROUND TOP BAG

1-79-211

Width	500mm
Height	330mm
Depth	310mm
Weight Capacity	25kg



WHEELED DUFFLE BAG

DWST1-79210

Width	305mm
Height	318mm
Length	699mm
Weight Capacity	25kg



MULTI PURPOSE

DWST1-75551

Width	270mm
Height	340mm
Depth	120mm



APRON

DWST1-75552

Width	120mm
Height	390mm
Depth	560mm



|106|



NAIL

DWST1-75650

Width	290mm
Height	360mm
Depth	180mm



TOOL BELT

DWST1-75651

Width	1390mm
Height	140mm
Depth	15mm



HAMMER & NAIL

DWST1-75652

Width	280mm
Height	370mm
Depth	170mm



DRILL HOLSTER

DWST1-75653

Width	170mm
Height	305mm
Depth	45mm



LEATHER BELT

DWST1-75661

Width	1409mm
Height	58mm
Denth	18mm



HAMMER LOOP

DWST1-75662

Width	125mm
Height	140mm
Depth	70mm





YEAR GUARANTEE UPON REGISTRATION
ANNI GARANZIA UPON REGISTRATION
JAHRE GARANTIE UPON REGISTRATION
ANS DE GARANTIE UPON REGISTRATION
XPONIA ERRYHEH UPON REGISTRATION
ANOS GARANTIA UPON REGISTRATION
JAAR GARANTIE UPON REGISTRATION
ANOS GARNTIA UPON REGISTRATION

The DEWALT 3 year guarantee is an extension of the standard 1 year warranty and offers security in case of manufacturing and material defects to DEWALT tools. To be eligible for the extended warranty you must register online within 4 weeks of purchase. Visit http://MyDeWALT.DeWALT.co.uk/3/ for a full list of products eligible for the extended warranty and to register your tool today.


HOW DOES IT WORK?

- 1. Log in to MyDeWALT at http://MyDeWALT.DeWALT.co.uk/3/. Create an account if you do not already have an existing one.
- 2. Register your product by entering the Product Model Number found on the rating label on the tool itself, and select an option from the drop-down list. For kits or product bundles, each individual item must be registered separately.
- Enter the Date Code (which is engraved inside the battery holder or on the underside of the product), followed by the Serial Number (which can be found on the tool's rating label). Finally enter your Reference (SKU) and the purchase location and date, and click 'Confirm'.
- 4. A summary page will appear, showing that your tool has been successfully registered on the MyDEWALT website. If the extended warranty is available, this will be indicated in green and you will be able to download your Warranty certificate.
- 5. If you ever need to claim on your extended warranty, you will be required to show your proof of purchase and printed Warranty certificate to your authorised DEWALT dealer prior to repair.



ONLINE SERVICES

www.2helpU.com



Visit our DEWALT service site for information on After Sales Services, including:

- Your nearest Authorized Repair Agent
- Frequently Asked Questions
- Technical Drawings
- Our Warranty Policy



You can also email us directly via the 'Ask a question' section. www.2helpu.com is also available from www.DEWALT.co.uk. Click on the 'Services' tab.



NATIONAL SERVICE CENTRE





At our DEWALT National Service Centre, we repair in excess of 20,000 products per year, and with over 150 years of DEWALT repair experience between our professional team of technicians, we are committed to our promise of 5-star service of quality, convenience and speed.





QUALITY

Our professional team of technicians are aided by state of the art testing equipment, allowing for an accurate and quality repair. This enables us to consistently maintain a high standard. All work is also backed by our best in class 6 month repair warranty.



CONVENIENCE

We offer a collection and delivery service to make the repair process of your DEWALT tool as smooth and seamless as possible for you. Our fantastic Customer Service team will help you through the process, giving you peace of mind that your tool is in safe hands.



SPEED

Having your tools back in action in the fastest time possible is our prime objective. Subject to parts availability, most repairs should not take more than 48 hours. For those smaller, urgent repairs we also provide an additional "while-uwait" service.



GENUINE PARTS

Every part used in our repairs are genuine
DEWALT spares, ensuring both the highest quality and a perfect fit every time. All of our genuine parts have the correct specification, and meet industry standards and regulations, guaranteeing optimum performance.



ONLINE SERVICES

Our Service website www.2helpU.com provides an additional wealth of information, easily accessible 24/7. Features includes FAQs, spare part details, technical information, our warranty policy and guides on recycling used tools



FOR AFTER SALES SERVICE AND TO LOCATE YOUR NEAREST AUTHORISED SERVICE AGENT PLEASE VISIT:

www.2helpU.com

1-70-321	99	DCB132	13	DCF887P2	21	DCM561P1S	33
1-70-322	99	DCB182	39	DCF888D2B	19	DCM561PBS	33
1-70-323	100	DCB183	40	DCF894N	22	DCM562P1	34
1-70-324	100, 102	DCB183B	16	DCF894P2	22	DCM562PB	34
1-70-349	100	DCB184	39	DCF897N	23	DCM563P1	34
1-70-362	102	DCB184B	16	DCF899HN	22	DCM563PB	34
1-79-208	107	DCB546	12	DCF899N	22	DCM565N	34
1-79-209	107	DCB547	13	DCF899P2	22	DCM565P1	34
1-79-211	107	DCC1054N	12	DCG405FN	25	DCM5713N	10
D21160	92	DCC1054T2	12	DCG405N	25	DCM5713X1	10
D21570K	93	DCD240N	12, 14	DCG405P2	25	DCM571N	10
D21580K	93	DCD240X2	12	DCG412M2	25	DCM571X1	10
D23700	77	DCD460N	11	DCG412N	25	DCM572N	11
D24000	90	DCD460T2	11	DCG414N	9	DCM572X1	11
D240001	90	DCD710D2	46	DCG414T2	9	DCM575N	11, 13
D25033K	60	DCD716D2	46	DCG426N	25	DCM575X1	11
D25133K	60	DCD740C1	24	DCG426P2	25	DCN660D2	27
D25134K	60	DCD740N	24	DCGG571M1	33	DCN660N	27
D25301D	63	DCD791P2	21	DCH253M2	24	DCN660P2	27
D25303DH	64	DCD796D2	20	DCH253N	24	DCN680D2	27
D25304DH	64	DCD796P2	20	DCH254M2	24	DCN680N	27
D25333	64	DCD797D2B	17, 20	DCH273	64	DCN681D2	28
D25333K	61	DCD985M2	20	DCH273P2	24	DCN681N	28
D25334	64	DCD991P2	21	DCH274P2	24	DCN682D2	28
D25334K	61	DCD996P2	20	DCH333	64	DCN682N	28
D25414KT	61	DCD997P2B	17	DCH333NT	8	DCN6901	26
D25481K	61	DCD997P2B-GB	20	DCH333X2	8	DCN692N	26
D25601K	62	DCE040	18	DCH334	64	DCN692P2	26
D25810K	62	DCE074D1R	52	DCH334N	9	DCN694N	27
D25899K	62	DCE079D1G	52	DCH334X2	9	DCN694P2	27
D25902K	63	DCE0825D1G	53	DCH481N	9	DCN8901-XJ	26
D25981	63	DCE0825D1G	54	DCH481X2	9	DCN8902-XJ	26
D259811	63	DCE088D1G	52	DCK2055T2T	14	DCN8903-XJ	26
D26200	82	DCE088D1G	5 <u>2</u>	DCK2056T2T	14	DCN8904-XJ	26
D26203	82	DCE089D1G	53	DCK2057T2T	14	DCN8905-XJ	26
D26204K	83	DCE089D1G	53 54	DCK2037121 DCK211D2T	49	DCN890N	26
D26410	85 85	DCE5601	33	DCK218D2T	48	DCN890P2	26
D26411	86	DCE580N	33	DCK229P2T	42	DCP580N	31
D26414	86	DCF610D2	47	DCK229F21 DCK2500P2B	18	DCP580P2	31
D26421		DCF6201	23	DCK266D2		DCR002	37
D26421 D26430	85	DCF620D2K		DCK266P2	41	DCR006	37
D26500K	84	-	23 23		41	-	36
	81	DCF620N		DCK276P2	41	DCR017	36
D27300	72	DCF620P2K	23	DCK623P3	43	DCR020	
D279058CL	96	DCF622N	23	DCK665P3T	43	DCR027	36
D28710	90	DCF622P2	23	DCK694P3	42	DCS310D2	47
D500910	96	DCF813D2	47	DCL040	37	DCS331M2	30
DCB090	41	DCF815D2	46	DCL043	38	DCS331N	30
DCB115	40	DCF880M2	22	DCL050	38	DCS350N	32
DCB118	13	DCF880N	22	DCL060	38	DCS355D2	31
DCB119	40	DCF887D2	21	DCL079-XJ	39	DCS355M2	31
DCB127	49	DCF887N	21	DCL510N	49	DCS355N	31

DCS365M2	28	DE3462
DCS365N	28	DE3471
DCS367N	30	DE3472
DCS371N	31	DE3473
DCS373N	29	DE3474
DCS380M2	30	DE3491
DCS380N	30	DE3494
DCS388N	7	DE3495
DCS388T2		DE3496
DCS391M2	29	DE6292
DCS391N2	29	DE7023
DCS397N DCS397N	10	DE7023
DCS397T2	10	DE7025
DCS491N	32	DE7027
DCS520N	6	DE7028
DCS520T2	6	DE7029
DCS551N	32	DE7030
DCS570N	29	DE7031
DCS570P2	29	DE7033
DCS575N	6	DE7035
DCS575T2	6	DE7260
DCS576N	6	DE7400
DCS576T2	6	DE7450
DCS7485N	8	DHS780N
DCS7485T2	8	DHS780T2
DCS777N	7	DT20658
DCS777T2	7	DT20658-Q2
DCS778N	7	DT2976-QZ
DCS778T2	7	DW03050
DCT410D1	48	DW03101
DCT410N	48	DW033
DCT414N	48	DW083K
DCV100	35	DW088
DCV517N	35	DW088CG
DCV584L	35	DW088CG
DE0714G	57	DW088K
DE0730	57	DW088KD
DE0730G	57	DW089
DE0734	58	DW089K
DE0735	57	DW089KD
DE0736	57	DW099S
DE0737	58	DW292
DE0772	55	DW294
DE0881	57	DW311K
DE0882	58	DW331K
DE0892	54	DW341K
DE0892G	54	DW615
DE2650	81	DW625EK
DE3454	70	DW680K
DE3460	70	DW682K
DE3461	70	DW717XPS
JEO∓01	10	אוווווט

70	DW721KN	73
70	DW729KN	73
70	DW733	72
70	DW743N	70
70	DW745	71
70	DW872	90
70	DW876	72
70	DWD024K	92
70	DWD524KS	92
78	DWE305PK	79
70	DWE315KT	76
70	DWE357K	80
70	DWE397	80
70	DWE4206	88
70	DWE4206K	88
70	DWE46105	89
70	DWE46150	88
70	DWE490	88
70	DWE492K	89
70	DWE550	76
70	DWE560	76
71	DWE575K	77
71	DWE576K	77
8	DWE6005	81
8	DWE6411	84
10	DWE6423	84
33	DWE7491	71
80	DWE74911	71
56	DWE74912	71
56	DW096PK	58
55	DWP352VS	85
55	DWP849X	89
54	DWS5021	78
53	DWS5022	
54	DWS5023	
53	DWS5025	
53	DWS5026	
54	DWS5029	
54	DWS5030	78
54	DWS5030	
_		78
56	DWS5032 DWS520K	78 70
93	DWS774	78
94		68
80	DWS777	68
79	DWS778	68
79	DWS780	69
82	DWST1-70702	104
83	DWST1-70703	102
81	DWST1-70704	102
83	DWST1-70705	103

69

DWST1-70706

DWST1-71194	103
DWST1-71195	104
DWST1-71196	106
DWST1-71228	104
DWST1-71229	105
DWST1-72364	106
DWST1-75522	98
DWST1-75551	107
DWST1-75552	107
DWST1-75650	108
DWST1-75651	108
DWST1-75652	108
DWST1-75653	108
DWST1-75654	99
DWST1-75661	108
DWST1-75662	108
DWST1-75663	98
DWST1-75668	100
DWST1-75676	73
DWST1-75694	102
DWST1-75694	106
DWST1-75774	105
DWST1-75799	105
DWST1-79210	107
DWST1-80123	101
DWST1-81042	106
DWST1-81045	106
DWST1-81055	101
DWST1-81079	98
DWST1-81079-GB	104
DWST1-81333	101
DWST7-97150	102
DWV901L	96
DWV902M	96
DWV9110	96
DWV9120	96
DWV9130	96
DWV9150	96
DWV9210	96
DWV9220	96
DWV9340	96
DWV9350	96
DWV9390	31
DWV9400	96
DWV9401	96
DWV9402	96
DWV9500	96

CONDITIONS OF SALE

JULY 2018

These conditions are written mainly in plain English. In these conditions "we" means Stanley Black & Decker UK Limited or Stanley Black and Decker Ireland, subsidiaries of Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland, and "you" means the person who accepts a quotation for the sale of the goods and whose order for the goods is accepted by Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland.

CATALOGUE ITEMS

- 1. Quotations and Orders
- a) All quotations are made and orders accepted under the following conditions. We must give
 written agreement to new or altered conditions. All orders accepted by us are under these
 conditions and not your conditions.
- b) Orders must be for boxes or cartons of items. We can vary order quantities to meet this condition.
- c) You cannot return any goods unless you have our permission, and only with an approved Returns Material Authority number.
- d) Each order will be delivered to one address. We will only deliver to your address and not a third party.
- e) Once we have processed an order you cannot cancel or change it. As we continuously improve our products we can alter specifications without telling you and in these circumstances you have no right to cancel any order to claim damages. Made to order goods cannot be cancelled under any circumstances once the order has been accepted.
- f) The price we charge you for the goods is the price of them on the date of your order. We will add V.A.T. to our prices at the proper rate on the date we send the goods.
- g) Any goods shall be sold subject only to these terms and conditions and, for the avoidance of doubt, shall not be sold upon any sale or return basis.

2 Delivery

- a) We will try to meet all delivery dates, but we are not legally liable for any delay in delivering or any losses caused by a delay. Time shall not be of the essence for delivery.
- b) Standard terms of delivery are DAP (Delivered at Place) unless otherwise stated.
- c) Unless we agree otherwise we will deliver goods by our standard delivery service choosing the most convenient and economical method available at the time of delivery. We will only make deliveries by other means if you ask us to and you pay.
- d) We will deliver and collect goods in normal working hours unless we have agreed otherwise. If this is inconvenient and you ask us to deliver or collect goods at a different time there will be a charge.
- e) Carriage charges are paid on all orders of a minimum net value. No orders, apart from spare parts will be accepted below this value.

Risk of Loss

- a) Once the goods have been delivered to your premises you are responsible for any loss or damage caused to the goods after you have received them.
- b) You must examine the goods immediately when they are delivered and tell us about any damage to, or shortages of, boxes and / or cartons within two working days. If the contents of any cartons are missing or damaged you should tell us within fifteen working days of the date of the invoice. When the goods are delivered you must also write details of any visible damage to the goods on the carrier's delivery sheet.

4. Accepting Goods

We will assume you have accepted the goods fifteen business days after they have been delivered unless you tell us about any complaints within that period. Also, if you, your agents, employees or licensees have used the goods, we will count this as accepting the goods.

5. Guarantees

- a) We only guarantee that when we deliver the goods they will not be damaged or have any faults. We are not liable for fair wear and tear.
- b) If you think that the goods are faulty you should tell us and wait for an instruction to either return the goods to a place we tell you or keep the goods for us to inspect. If we accept that there is a fault we will either repair or replace the faulty part or parts or refund the original price of the goods.
- c) The situation described in 5 (b) above shall not apply to the following:
- any goods which have been repaired or altered by somebody who isn't an employee of ours.
- 2) goods which have been mixed with other goods or used to create other products.
- any goods which, in our opinion, have been subject to any accident or to damage or which have been improperly stored, maintained or used.

d) We are not liable for the following:

- 1) any direct loss or damage except the liabilities we have already mentioned.
- any indirect, consequential or incidental loss or damage of any kind (including loss of profits, revenue or contracts) or for any damage to or destruction of any property.
- injury to, or the death of, any person unless that injury or death is caused by our carelessness or that of our employees.
- e) Our only guarantees, conditions and liabilities are those given in this document.
- f) You must indemnify us against all claims, actions, costs, losses, damages or expenses caused by or in connection with the goods unless we are liable under these conditions.
- g) If we repair or replace any goods under 5(b) we will take the date that the repair is finished or the goods are replaced to be the date on which the goods were delivered.

6. 'Force Majeure'

Without prejudice to any other terms of this agreement we are not liable for any act or omission or if we do not enforce, or we delay enforcing any condition in this Agreement because of any circumstances or causes beyond our control.

7. Paymer

- a) Payment is due at the end of the following month from the date of Invoice unless otherwise advised.
- b) If you delay paying for no good reason we may choose to suspend all deliveries to you until we have received all payments which are due.
- c) If you do not pay within our terms we reserve the right to charge interest in accordance with the provisions and rates provided in The Late Payment of Commercial Debts (Interest) Art 1998

d) If you disagree with an invoice you must tell us about this within 7 days of receiving the goods, and that if our investigation confirms that your query is justified you do not need to pay for the amounts disputed on the invoice or any interest due.

3. Owning the Goods

Ownership and title to the Goods shall remain with Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland until

a) You have paid in full for the goods.

- b) You have made full payment for any other goods or products supplied under any contracts or on any account whatsoever between Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland and all other sums whatever due from you to Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland have been paid in full.
- c) If you pay by cheque, bill of exchange or promissory note, we own the property until the same has been honoured. We may apply any payments you make to any of your invoices which we see fit
- d) Until you have paid for the goods you will be acting as our fiduciary agent and bailee. You must keep records of the goods and store the goods in a way that makes them clearly identifiable as being our property. These goods should be insured by you or as part of your general insurance cover. We will assume that any goods you have which we supplied belong to us (unless you can prove otherwise)

e) If you:

1) make any arrangement with your creditors;

2) go into liquidation;

3) appoint a receiver to manage all or part of your assets;

4) fail to make payment for the goods; or

- 5) cannot, in our opinion pay your debts; then, we have the following rights:
- 1) to enter any property and repossess the goods without giving you notice.
- to give you written notice that you must not sell or get rid of the goods until we have received full payment for them.
- 3) to cancel any undelivered goods and stop any goods that are being transported to
- f) At any time we may give you the ownership of the goods if we give you notice of our intention to do so. Under condition 8 (c) ownership of the goods will pass to you when you sell or get rid of goods which we own immediately before you sold or got rid of them.
- g) We may sue you for the price of the goods when the payment is due even though the ownership of the goods may not have passed to you.
- h) In any circumstances prevailing under clause 8e) (1)-(5) then we shall in respect of any rebate arrangement with you exercise our unfettered right to offset any sums due from you against any amount on our accounts receivable ledger by way of credit note under any rebate arrangement, in full or part satisfaction of any sum due to the Company by you.
- i) In respect of clause 8h) you the Customer undertake to keep us informed upon written 14 day notice of any event or circumstance that places your business in a precarious financial position which may lead to an administration order bankruptcy or liquidation and we undertake to provide you with written 7 day notice of our intention to exercise our rights by way of right of offset.
- We may impose restrictions on the reselling of goods, subject to U.K. and E.E.C. trading laws.
- If any condition or part of condition in this Agreement is not valid or cannot be enforced this will not affect any part of the condition or Agreement.
- 11. If the ownership of your company changes we will automatically cancel this Agreement and negotiate a new one.
- 12. These conditions of sale only apply to your company and your own branch companies which carry out similar trade. They are not offered to your associate companies, either within or outside its trade unless we agreed this when we were negotiating this Agreement.
- 13. You shall and shall procure that your officers, employees, agents, sub-contractors and any other persons who perform services for or on behalf of you in connection with this Agreement shall:
- a) not commit any act or omission which causes or could cause it or Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland to breach or commit an offence under any laws relating to anti-bribery or anti-corruption;
- b) comply with Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland anticorruption policy as updated from time to time, a current copy of which is available upon request;
- c) keep accurate and up to date records showing all payments made and received and all other advantages given and received by it in connection with this Agreement and the steps it takes to comply with this condition and permit Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland to inspect those records as required.
- d) promptly notify Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland of any request or demand for any financial or other advantage received by it; and any financial or other advantage it gives or intends to give whether directly or indirectly in connection with this Agreement; and
- e) promptly notify Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland of any breach of this condition. Stanley Black & Decker UK Limited or Stanley Black & Decker Ireland may terminate this Agreement immediately by giving notice to that effect to you if you are in breach of condition 13.

Governing La

This Agreement, for all purposes, is governed and construed by the laws of England and Wales and both parties agree to submit to the exclusive jurisdiction of the Courts of England and Wales.

Unless we have agreed otherwise in writing, our standard conditions of sale also apply.



DEWALT UK®
210 Bath Road, Slough,
Berkshire SL1 3YD
Customer Service Phone:
01753 567055

Fax: 01753 572112

dewalt.com









All rights reserved. Neither this catalogue nor its text, illustrations, drawings or any part thereof, may be reproduced, stored in a retrieval system, photocopied, recorded or transmitted in any form, whether electronic or otherwise, without our consent. To the best of our knowledge, all descriptions and illustrations contained in this catalogue are correct at the time of going to print. We cannot, however, be held liable for any inaccuracies of description or illustration and reserve the right to change specifications without notification.