




RECTORSEAL[®]

ELECTRICAL PRODUCT CATALOG



Wire Pulling Tools
Wire Pulling Devices
Firestopping
Pipe Joining
Other Products



THANK YOU.



RectorSeal is proud to have been partnered with the trades through product development and innovation for over 75 years. Your continued trust and patronage of our products and services will never be taken for granted.

David M. Smith

President, RectorSeal Corporation

Catalog Contents & Product Features

RectorSeal® **Wire Pulling Tools** are strong and fast, making wire pulling amazingly easy. From an incredibly strong light-weight cable puller and low-profile fast cutting knockout tools and fully articulating hydraulic punchers to fast ratcheting cable cutters. RectorSeal® Wire Pulling Tools make the job easy with no wasted time or material.

5-11

RectorSeal® **Wire Pulling Devices** reduce labor cost per pull and significantly increase productivity by completing more pulls per day. With both reusable Wire Snagger® and Single-Use Wire Grabber™, wire pulls can be set-up and torn down in less than 5 minutes. Wire Snagger® is a stainless-steel, spring activated teeth device for wire from 2/0 to 750 MCM to use over and over. Single-Use Wire Grabber™ works on 8 AWG thru 1000 MCM wire, rated for copper and aluminum and is disposable with wire.

12-18

Metacaulk® **Firestopping** the worldwide leader in firestop technology. Specifically designed caulks and pre-fabricated devices fill voids in construction joints and around penetrations in fire-rated walls or floors preventing the spread of fire.

19-26

RectorSeal® offers **Low-VOC Solvent Cements, Primers and Cleaners** for a variety of applications. You can rely on the high-quality, consistent performance of these products. RectorSeal® **Pipe Thread Sealants** are the finest in the industry, tested extensively for quality control to insure strong and reliable performance.

27-32

Other Products Duct Seal, Cutting oils, Anti-seize compound, Specialty sealant caulks & Specialty cleaners and degreasers.

33-38

Index

39



Scan for RectorSeal® homepage

Wire Pulling Tools

StrongArm™ •

K.O. Puncher™ •

Roundhouse™ •

UpperCut™ •

Tri-Point™ •

Cups & Cutters •





WIRE PULLING TOOLS

StrongArm™

Lightweight 4000 lbs. cable puller

Code	Description	Qty.
97100	StrongArm	1



Scan for
Instructions


FEATURES

- Two speeds: 80 ft/m & 20 ft/m
- Folds for easy handling & storage with an easy to use hinged frame
- Self-positioning base requires no anchoring for most pulls
- Quick disconnect pins
- Removable base can hook to most trailer hitches

Application • Quick & practical one-man operation; Sets up & locks into position in 60 seconds • Takes up only 42" of space when folded, yet its unique swivel head can extend beyond 10' to meet the demands of underground or overhead pulls

Recommended for

- Pulling cable thru conduit
- Ground level cable pulling (w/ Tripod Adapter Kit)





Tripod Adapter Kit

For manhole or ground level wire pulling


Code	Description	Qty.
97103	Tripod adapter kit	1

FEATURES

- Quickly attaches to StrongArm
- Sets up in less than 2 minutes
- Use to pull out extra wire

Application • Designed for pulling from transformer pads, transformer vaults, manholes and meter bases • Tripod adapter uses struts (not included) for its legs, allowing you to decide what length works best for the job

Recommended for
• Use with StrongArm™



WIRE PULLING TOOLS

Continued

K.O. Puncher™

Drill activated knockout tool

Code	Description	Qty.
97113	K.O. Puncher	1
97119	Punch Adapter	1



Scan for Instructions

FEATURES

- Fits any std. cordless drill
- 2-3 times faster than hydraulic punches; No oil leaks
- Use adapter for other brands' cups & cutters
- Works in freezing temp. to -20°F

Application • Acts as an attachment between the draw stud, die-set and your cordless drill • Simple set-up and fast cutting

- Delivers quick knockouts in 5 seconds

Recommended for

- Steel & stainless steel electrical boxes



K.O. Puncher™ Kit

Complete knockout kit

Code	Description	Qty.
97115	Standard Kit ½" - 2-½"	1
97117	Deluxe Kit ½" - 4"	1

FEATURES

- Fits any std. cordless drill
- 2-3 times faster than hydraulic punches; No oil leaks
- Wide range of sizes
- Works in freezing temp. to -20°F

Application • Everything you need to complete quick & simple knockouts

Recommended for

- Up to 10 gauge mild steel • Up to 14 gauge stainless steel electrical boxes

Includes • Standard: (1) K.O. Puncher, (7) ½" - 2½" cups & cutters, (2) Tri-Points, (2) draw studs, (1) punch adapter and case

- Deluxe: (1) K.O. Puncher, (10) ½" - 4" cups & cutters, (2) Tri-Points, (2) draw studs, (1) punch adapter and case



Roundhouse™

Fully articulating hydraulic puncher

Code	Description	Qty.
97140	Roundhouse	1
97119	Punch Adapter	1



Scan for Instructions


FEATURES

- Head swivels up, down & around
- Fits in tight & hard to reach places
- Punch from any direction
- Use adapter for other brands' cups & cutters
- No leaks or repairs on hoses

Application • The only self-contained hydraulic punching tool made for use with cups and cutters up to 4"

Recommended for

- Steel & stainless steel electrical boxes



Roundhouse™ Kit

Hydraulic punch kit

Code	Description	Qty.
97143	Standard Kit ½" - 2-½"	1
97145	Deluxe Kit ½" - 4"	1

FEATURES

- Head swivels up, down & around
- Fits in tight & hard to reach places
- Punch from any direction
- Wide range of sizes
- No leaks or repairs on hoses

Application • Everything you need to complete quick & simple knockouts

Recommended for

- Up to 10 gauge mild steel
- Up to 14 gauge stainless steel electrical boxes

Includes • Standard: (1) Roundhouse, (7) ½" - 2½" cups & cutters, (2) Tri-Points, (2) draw studs, (1) punch adapter and case

- Deluxe: (1) Roundhouse, (10) ½" - 4" cups & cutters, (2) Tri-Points, (2) draw studs, (1) punch adapter and case



WIRE PULLING TOOLS

Continued

UpperCut™ I Handheld cable cutter

Code	Description	Qty.
97105	UpperCut I	3



Scan for Instructions

FEATURES

- Honed steel alloy blades
- 6-1/4" locking, telescoping handles

Application • Slices thru wire & cable without waste • Leverage-multiplying ratcheting system allows for smooth operation

Recommended for • Up to 750 MCM Copper & Aluminum wire



UpperCut™ II Utility grade cable cutter

Code	Description	Qty.
97106	UpperCut II	1



Scan for Instructions

FEATURES

- Honed steel alloy blades
- 14-1/4" locking, telescoping handles

Application • Slices thru wire & cable without waste • Leverage-multiplying ratcheting system allows for smooth operation

Recommended for • Up to 1000 MCM Copper & Aluminum wire



UpperCut™ III Utility grade cable cutter

Code	Description	Qty.
97108	UpperCut III	1




Scan for Instructions

FEATURES

- Honed steel alloy blades
- 14-1/4" fixed handles

Application • Slices thru wire & cable without waste • Leverage-multiplying ratcheting system allows for smooth operation

Recommended for • Up to 1000 MCM Copper & Aluminum wire



Cups & Cutters

3 point, deep knockout punch

Code	Description	Qty.
97114	1/2"	6
97116	3/4"	6
97118	1"	6
97120	1-1/4"	6
97121	1-1/2"	6
97122	2"	6
97127	2-1/2"	6
97128	3"	2
97129	3-1/2"	2
97131	4"	2

FEATURES

- Innovative 3 cutting surfaces
- Cuts faster
- Stays cooler
- Longer lasting tool life
- Wide range of sizes

Application • For making holes in panel boxes for attaching conduit

Recommended for

- Up to 10 gauge mild steel
- Up to 14 gauge stainless steel electrical boxes

See ordering chart for other available sizes



Tri-Point™

3 point step bits

Code	Description	Qty.
97123	7/8" bit	6
97125	1-1/8" bit	6


FEATURES

- Innovative 3 cutting surfaces
- Speeds thru cuts faster than 2 point bits
- Requires less torque
- Runs cooler

Application • For making starter holes for knockout draw studs

Recommended for

- Steel & stainless steel electrical boxes



Double Braid Composite Rope

Code	Description	Qty.
97148	9/16" x 300'	1
97150	9/16" x 600'	1

FEATURES

- 4000 lbs. heavy duty rope; Specially designed for use with StrongArm cable puller
- High strength, low stretch
- Excellent resistance to UV rays, chemicals & abrasion
- Rot, mold & mildew resistant
- Factory spliced pulling eye at each end
- 16,000 lbs. avg. breaking strength



Mule Tape

Code	Description	Qty.
97153	3000'	1

FEATURES

- 1250 lbs. light pulling load
- High strength, low stretch
- Easily blown through conduits or ducts
- Printed sequential footage markings for accurate measurements



For Wire Pulling Tools accessories & replacement parts, visit www.rectorseal.com/qr/wpa.html or scan this code.





Wire Pulling Devices

- Wire Snagger®
- Single-Use Wire Grabber™
- Accessories



WIRE SNAGGER®

Wire Snagger® Master Set

Single lanyard set

Code	Description	Qty.
97958	WS Master Set	1

FEATURES

- Heat-treated stainless steel
- Spring activated teeth
- Navigates bends in conduit
- Reduce set up & tear down
- Reusable - Long tool life
- Can be rebuilt

Application • Complete set to handle most wire pulling needs (20 tools & accessories) • Easy to use wire pulling device
 • Save time & reduce labor costs • No need to strip, tape, trim or tie wires • Longer lanyards reduce congestion in conduit

Recommended for • THHN & XHHW Copper Wire
 • THHN & XHHW Aluminum Wire

Includes • (4) WS-3/0 w/ 13", 20", 27" & 34" lanyards
 • (4) WS-4/0 w/ 13", 20", 27" & 34" lanyards
 • (4) WS-350 w/ 13", 22", 31" & 40" lanyards
 • (4) WS-500 w/ 13", 22", 31" & 40" lanyards
 • (4) WS-600 w/ 13", 22", 31" & 40" lanyards
 • (1) 3000 lbs. clevis clip • (1) 11,000 lbs. clevis clip
 • (1) 50" lanyard extension



US Patent No 6,883,782; 7,128,306; 7,246,789; 7,478,794; 7,934,697

Clevis Clip

Join or link multiple lanyards

Code	Description	Qty.
97949	3000 lbs. 1-1/4"	6
97998	11,000 lbs. 1-3/4" x 3-1/2"	2

FEATURES

- Made of hardened steel
- Connect extensions (3000 lbs.)
- Connect multiple tools to pulling rope (11,000 lbs.)



Lanyard Extension

Add length or additional tool

Code	Description	Qty.
97948	50" extension	6

FEATURES

- Pull more than 4 tools on a single rope





WIRE SNAGGER®

Continued

Wire Snagger®

Reusable single lanyard device with spring loaded teeth

Wire Pulling Tools

Wire Pulling Devices

Firestopping

Pipe Joining

Other Products

WS-3/0



Code	Description	Qty.
97961	WS-3/0 13" wire lanyard	1
97962	WS-3/0 20" wire lanyard	1
97963	WS-3/0 27" wire lanyard	1
97964	WS-3/0 34" wire lanyard	1

WS-4/0



Code	Description	Qty.
97965	WS-4/0 13" wire lanyard	1
97966	WS-4/0 20" wire lanyard	1
97967	WS-4/0 27" wire lanyard	1
97968	WS-4/0 34" wire lanyard	1

WS-350



Code	Description	Qty.
97969	WS-350 13" wire lanyard	1
97970	WS-350 22" wire lanyard	1
97971	WS-350 31" wire lanyard	1
97972	WS-350 40" wire lanyard	1

WS-500



Code	Description	Qty.
97973	WS-500 13" wire lanyard	1
97974	WS-500 22" wire lanyard	1
97975	WS-500 31" wire lanyard	1
97976	WS-500 40" wire lanyard	1

WS-600



Code	Description	Qty.
97977	WS-600 13" wire lanyard	1
97978	WS-600 22" wire lanyard	1
97979	WS-600 31" wire lanyard	1
97980	WS-600 40" wire lanyard	1

WS-750



Code	Description	Qty.
97924	WS-750 6" wire lanyard	1
97929	WS-750 18" wire lanyard	1
97932	WS-750 30" wire lanyard	1
97935	WS-750 42" wire lanyard	1

US Patent Number 6,883,782; 7,128,306; 7,246,789; 7,478,794; 7,934,697

Contact: RectorSeal®

☎ 713-263-8001 | 800-231-3345

☎ 713-263-7577 | 800-441-0051

🌐 www.rectorseal.com

WIRE SNAGGER® LOAD CHART

WIRE SNAGGER® SPECIFICATIONS FOR THHN & XHHW COPPER WIRE													
Wire Snagger®	Wire Size	Max Intermittent Load (lbs)		Max Continuous Load (lbs)		Min conductor dia. (in)	Max conductor dia. (in)	Max overall dia. (in)	Minimum EMT Conduit Size (in)				
		One Tool	Five Tools	One Tool	Five Tools				1 Wire	2 Wires	3 Wires	4 Wires	5 Wires
WS 3/0	2/0	1000	5000	600	3000	0.376	0.470	0.590	1-½	2	2	2*	2-½
	3/0	1000	5000	600	3000				1-½	2	2*	2*	2-½
WS 4/0	4/0	1600	8000	1000	5000	0.475	0.575	0.720	2	2-½	2-½	2-½	2-½*
	250 MCM	2400	12000	1400	7000				2	2-½	2-½	2-½	2-½*
WS 350	350 MCM	2400	12000	1400	7000	0.616	0.681	0.825	2	2-½	2-½	2-½	3
WS 500	500 MCM	3600	18000	2200	11000	0.736	0.813	0.960	2-½	3	3	3*	3-½
WS 600	600 MCM	3600	18000	2200	11000	0.813	0.893	1.080	2-½	3	3*	3-½	4
WS 750	750 MCM	3600	18000	2200	11000	0.908	0.998	1.156	2-½	3*	3-½	4	-

For use on THHN & XHHN copper wire only.

*May require special service (such as removing bushing and installing extra guide pulleys) when pulling Max diameter wires through Min size conduit.

WIRE SNAGGER® SPECIFICATIONS FOR THHN & XHHW ALUMINUM BUILDING WIRE														
Wire Snagger®	Wire Size	Max Number Strands ¹	Max Intermittent Load (lbs)		Max Continuous Load (lbs)		Min conductor dia. (in)	Max conductor dia. (in)	Min insulation dia. (in)	Max insulation dia. (in)	Minimum EMT Conduit Size (in)			
			One Tool	Four Tools	One Tool	Four Tools					1 Wire	2 Wires	3 Wires	4 Wires
WS 3/0	2/0	12	800	3200	600	2400	0.379	0.461	0.489	0.589	1-½	2	2	2
	3/0	18	900	3600	700	2800					1-½	2	2	2
	3/0 (E194343) ²	19	550	2200	400	1600					1-½	2	2	2
	4/0 (Simpull)	19	1000	4000	750	3000					2	2-½	2-½	2-½
WS 4/0	4/0	19	1000	4000	750	3000	0.461	0.520	0.589	0.655	2	2-½	2-½	2-½
	250 MCM	23	1000	4000	750	3000					2	2-½	2-½	2-½
WS 350	250 MCM	35	900	3600	650	2600	0.600	0.659	0.746	0.789	2	2-½	2-½	2-½
	350 MCM	35	2000	8000	1400	5600					2	2-½	2-½	2-½
	350 MCM	37	1600	6400	1200	4800					2	2-½	2-½	2-½
WS 500	400 MCM	35	2600	10400	1900	7600	0.720	0.795	0.866	0.971	2	2-½	2-½	2-½
	500 MCM (E194343) ²	35	1400	5600	1000	4000					2-½	3	3	3
	500 MCM	37	3000	12000	2200	8800					2-½	3	3	3
WS 600	600 MCM (Simpull)	41	3300	13200	2200	8800	0.813	0.911	0.973	1.071	2-½	3	3	3-½
	600 MCM	61	2600	10400	1900	7600					2-½	3	3	3-½
WS 750	750 MCM	58	2800	11200	2100	8400	0.963	1.002	1.139	1.162	3	3-½	4	4

Notes:

1. Pulling loads for any given wire size decreases as the number of strands increase.
2. Pulling loads vary according to material properties.
3. Contact RectorSeal for wire configurations different from those depicted in this table.



SINGLE-USE WIRE GRABBER™

Single-Use Wire Grabber™

Disposable single lanyard crimp-on device

FEATURES

- Low initial cost
- Lugs are disposable w/ wire
- Save time & money
- Secure with crimping tool
- Bands on body match crimping die size color


- Application** • Single-use tool reduces set-up time & waste • Compact tool body easily pulls around bends
- Staggered lanyards reduce pulling friction
- Recommended for** • THHN & XHHW Copper Wire
- THHN & XHHW Aluminum Wire • Medium & High voltage wire

SU 8 AWG



Code	Description	Qty.
98120	SU8AWG 11" wire lanyard	6
98117	SU8AWG 15" wire lanyard	6
98118	SU8AWG 19" wire lanyard	6
98119	SU8AWG 23" wire lanyard	6

SU 6 AWG




Code	Description	Qty.
98137	SU6AWG 11" wire lanyard	6
98138	SU6AWG 15" wire lanyard	6
98139	SU6AWG 19" wire lanyard	6
98140	SU6AWG 23" wire lanyard	6

SU 4 AWG



Code	Description	Qty.
98133	SU4AWG 11" wire lanyard	6
98134	SU4AWG 15" wire lanyard	6
98135	SU4AWG 19" wire lanyard	6
98136	SU4AWG 23" wire lanyard	6

SU 3 AWG




Code	Description	Qty.
98129	SU3AWG 11" wire lanyard	6
98130	SU3AWG 15" wire lanyard	6
98131	SU3AWG 19" wire lanyard	6
98132	SU3AWG 23" wire lanyard	6

SU 2 AWG




Code	Description	Qty.
98125	SU2AWG 11" wire lanyard	6
98126	SU2AWG 15" wire lanyard	6
98127	SU2AWG 19" wire lanyard	6
98128	SU2AWG 23" wire lanyard	6

SU 1 AWG



Code	Description	Qty.
98121	SU1AWG 11" wire lanyard	6
98122	SU1AWG 15" wire lanyard	6
98123	SU1AWG 19" wire lanyard	6
98124	SU1AWG 23" wire lanyard	6

SU 1/0 AWG




Code	Description	Qty.
98141	SU1/0AWG 14" wire lanyard	6
98142	SU1/0AWG 21" wire lanyard	6
98143	SU1/0AWG 28" wire lanyard	6
98144	SU1/0AWG 35" wire lanyard	6

SU 2/0 AWG




Code	Description	Qty.
98145	SU2/0AWG 14" wire lanyard	6
98146	SU2/0AWG 21" wire lanyard	6
98147	SU2/0AWG 28" wire lanyard	6
98148	SU2/0AWG 35" wire lanyard	6

SU 3/0 AWG



Code	Description	Qty.
98149	SU3/0AWG 14" wire lanyard	6
98150	SU3/0AWG 21" wire lanyard	6
98151	SU3/0AWG 28" wire lanyard	6
98152	SU3/0AWG 35" wire lanyard	6

SU 4/0 AWG



Code	Description	Qty.
98153	SU4/0AWG 14" wire lanyard	6
98154	SU4/0AWG 21" wire lanyard	6
98155	SU4/0AWG 28" wire lanyard	6
98156	SU4/0AWG 35" wire lanyard	6

SU 250 MCM



Code	Description	Qty.
98157	SU250MCM 14" wire lanyard	6
98158	SU250MCM 21" wire lanyard	6
98159	SU250MCM 28" wire lanyard	6
98160	SU250MCM 35" wire lanyard	6

SU 300 MCM




Code	Description	Qty.
98161	SU300MCM 14" wire lanyard	6
98162	SU300MCM 21" wire lanyard	6
98163	SU300MCM 28" wire lanyard	6
98164	SU300MCM 35" wire lanyard	6

SU 350 MCM



Code	Description	Qty.
98165	SU350MCM 14" wire lanyard	6
98166	SU350MCM 21" wire lanyard	6
98167	SU350MCM 28" wire lanyard	6
98168	SU350MCM 35" wire lanyard	6

SU 400 MCM




Code	Description	Qty.
98169	SU400MCM 14" wire lanyard	6
98170	SU400MCM 21" wire lanyard	6
98171	SU400MCM 28" wire lanyard	6
98172	SU400MCM 35" wire lanyard	6

SU 500 MCM



Code	Description	Qty.
98173	SU500MCM 14" wire lanyard	6
98174	SU500MCM 21" wire lanyard	6
98175	SU500MCM 28" wire lanyard	6
98176	SU500MCM 35" wire lanyard	6

SU 600 MCM



Code	Description	Qty.
98177	SU600MCM 14" wire lanyard	6
98178	SU600MCM 21" wire lanyard	6
98179	SU600MCM 28" wire lanyard	6
98180	SU600MCM 35" wire lanyard	6

SU 750 MCM



Code	Description	Qty.
98181	SU750MCM 14" wire lanyard	6
98182	SU750MCM 21" wire lanyard	6
98183	SU750MCM 28" wire lanyard	6
98184	SU750MCM 35" wire lanyard	6

SU 1000 MCM



Code	Description	Qty.
98185	SU1000MCM 14" wire lanyard	6
98186	SU1000MCM 21" wire lanyard	6
98187	SU1000MCM 28" wire lanyard	6
98188	SU1000MCM 35" wire lanyard	6

SINGLE-USE WIRE GRABBER™ LOAD CHART

WIRE GRABBER™ SPECIFICATIONS FOR COPPER & ALUMINUM WIRE											
Single-Use Wire Grabber™	Wire Size	Max Load (lbs)		Min conductor dia. (in)	Max conductor dia. (in)	Minimum EMT Conduit Size (in)					Crimper
		One Tool	Five Tools			1 Wire	2 Wires	3 Wires	4 Wires	5 Wires	
SU 8	8 AWG	130	650	0.134	0.146	-	-	-	-	-	12 to 15 ton Die Crimper
SU 6	6 AWG	210	1050	0.169	0.184	-	-	-	-	-	
SU 4	4 AWG	300	1500	0.213	0.232	-	-	-	-	-	
SU 3	3 AWG	400	2000	0.238	0.260	-	-	-	-	-	
SU 2	2 AWG	500	2500	0.268	0.292	-	-	-	-	-	
SU 1	1 AWG	669	3345	0.299	0.332	-	-	-	-	-	
SU 1/0	1/0 AWG	844	4220	0.336	0.373	1	1-¼	1-¼	1-½	2	
SU 2/0	2/0 AWG	1000	5000	0.376	0.419	1	1-¼	1-½	2	2	
SU 3/0	3/0 AWG	1250	6250	0.423	0.470	1	1-½	1-½	2	2-½	
SU 4/0	4/0 AWG	1650	8250	0.475	0.528	1-¼	1-½	2	2	2-½	
SU 250	250 MCM	2000	10000	0.520	0.575	1-¼	2	2	2-½	2-½	
SU 300	300 MCM	2400	12000	0.570	0.631	1-¼	2	2	2-½	2-½	
SU 350	350 MCM	2400	12000	0.616	0.681	1-½	2	2-½	2-½	3	
SU 400	400 MCM	2400	12000	0.659	0.728	1-½	2-½	2-½	2-½	3	
SU 500	500 MCM	4000	20000	0.736	0.813	1-½	2-½	2-½	3	3-½	
SU 600	600 MCM	4200	21000	0.813	0.893	2	2-½	3	3	3-½	
SU 750	750 MCM	4300	21500	0.908	0.998	2	3	3	3-½	4	
SU 1000	1000 MCM	5000	25000	1.060	1.153	2	3	3-½	4	4-½	15 ton Die Crimper

For use on THHN & XHHN copper & aluminum wire only.

*May require special service (such as removing bushing and installing extra guide pulleys) when pulling Max diameter wires through Min size conduit.

Firestopping

Intumescent Sealants •

Pass-Thru Devices •

Pipe Collars and Sleeves •

Electrical Box Firestop •


Putty Sticks and Pads •

Cable Coating •

Joint Strip •



METACAUK® FIRESTOP SEALANTS



Metacaulk® 1000

Intumescent, water-based firestop sealant

Code	Description	Qty.
66640	10.3 oz. cartridge	12
66303	30 oz. cartridge	12
66312	20.2 oz. sausage pack	12
66305	1 gal.	4
66307	2 gal.	1
66309	5 gal.	1

Application • Will prevent the spread of fire through joint openings and through-penetrations
 • No dilution or mixing required • Can be used in areas under constant vibration and movement
 • Use in fire-rated gypsum wallboard partitions, concrete walls or floors, wood floors and concrete or corrugated steel deck floor/ceiling assemblies

Recommended for • Metal • Insulated
 • Fiberglass & plastic pipes • Wall construction joints • Power & telephone cables



FEATURES

- UL Classified systems up to 4 hrs.
- Highly intumescent
- Excellent freeze-thaw
- For interior use - paintable
- VOC compliant
- STC rating 62
- Meets ASTM E 814, UL 1479 & UL 2079 standards

See ordering chart for container sizes available.



*"FBC™ System Compatible" indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings.

**"FBC", FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of the Lubrizol Corporation.

For Firestopping accessories, visit www.rectorseal.com/qr/mfa.html or scan this code.



Metacaulk® MC 150+

General purpose firestop sealant

Code	Description	Qty.
66648	10.3 oz. cartridge	12
66383	30 oz. cartridge	12
66385	20.2 oz. sausage pack	12
66389	5 gal.	1



FEATURES

- Water-based - VOC compliant
- Excellent freeze-thaw
- For interior use - paintable
- Use for most common applications
- STC rating 51

Application • One component, general purpose fire-rated sealant and smoke seal for construction joints and through-penetrations on both horizontal and vertical surfaces

- Non-sag caulking grade sealant that is easy to apply as well as to retrofit
- Can be used in areas under constant vibration or movement

Recommended for

- Metal
- Insulated
- Fiberglass and plastic pipes
- Wall construction joints
- Power and telephone cables



Metacaulk® 350i

Elastomeric seal firestop sealant

Code	Description	Qty.
66616	10.3 oz. cartridge	12
66611	20.2 oz. sausage pack	12
66613	5 gal.	1



FEATURES

- Sound rated
- Excellent freeze-thaw
- For interior use - paintable
- STC rating 53

Application • One component, general purpose sealant and smoke seal

- Intumescent, water-based, non-sag caulking grade sealant that is easy to apply and great for retrofits
- Suitable for dynamic movement

Recommended for

- Metal
- Insulated
- Fiberglass & plastic pipes
- Wall construction joints
- Power & telephone cables



Metacaulk® 835+

Elastomeric, silicone firestop sealant

Code	Description	Qty.
66645	10.15 oz. cartridge	12
66019	5 gal.	1



FEATURES

- Exterior / Interior use
- Water resistant
- STC rating 55

Application • Used in systems where dynamic movement is expected

- Resistant to chemical exposure

Recommended for

- Cable and cable trays
- EMT
- Insulated and uninsulated steel pipe
- Construction and control joints
- Interior expansion joints



Also available in
5 gal. pail



METACALK® FIRESTOP DEVICES

Metacaulk® Pass-Thru

Pre-firestopped, shaped sleeves

Code	Description	Qty.
66770	2-1/2" square	6
66773	4" square	6
66776	2" round	6
66779	4" round	6
66740	2-1/2" single sq. bracket	6
66743	2-1/2" double sq. bracket	3
66746	2-1/2" triple sq. bracket	2
66749	2-1/2" sixplex sq. bracket	2
66752	4" single sq. bracket	6
66755	4" double sq. bracket	3
66758	4" triple sq. bracket	2
66761	4" sixplex sq. bracket	1
66764	2" round bracket	6
66767	4" round bracket	6

Application • Seals cables or pipes that penetrate thru 1 & 2 hour fire rated walls & floors • Square or round shaped steel sleeves with intumescent material • Opens for easy installation, retrofit or removal of cables

Recommended for • Electrical • DataComm • Communication cables • Pipes



US Patent No. 6,207,085



FEATURES

- Easy to install & change cables
- Great for retrofit
- Highly intumescent
- Industry leading "L" rating


Metacaulk® Pipe Collars

Prefabricated firestop system

Code	Description	Qty.
66352	1-1/2"	12
66353	2"	12
66350	3"	6
66351	4"	6
66354	6"	2

Application • UL classified for both open and closed pipe systems • Simple locking mechanism for easy installation

Recommended for • PVC • CPVC • ABS • PVC foam core • ABS foam core • FRPP • PEX pipe • Electrical cable • Contact Tech Services for other options



U.S. Patent No. 6,207,085



FEATURES

- No measurements of material
- Fits in limited access areas
- 25% reduction of installation time



Metacaulk® Intumescent Sleeve


Firestop seal

Code	Description	Qty.
66584	For 2", 3" & 4" Pipe	6
66582	For 6" & 8" Pipe	1

Application • Firestop through penetrations with a single sleeve • Ideal for combustible pipes penetrating a concrete fluted deck assembly

Recommended for • PVC • cc-PVC • CPVC • FRPP • PP • ABS • PP-R • Rigid non-metallic conduit installations

US Patent No. 6,207,085



FEATURES

- No steel bolts or fasteners
- Can be retrofitted
- Flexible



Cover Guard™

Fire-rated gasket for electrical boxes


Code	Description	Qty.
66270	Double receptacle	50
66272	Single receptacle	50
66274	Double switch	50
66276	Single switch	50
66265	Single decor	50
66266	Double decor	50



FEATURES

- Reduces sound transmission
- Easy to install
- Highly intumescent
- STC rating 54

Application • A single component fire-rated gasket for use with electrical boxes to comply with the “24 inch rule” • Fits under the cover plate and does not take up volume



US Patent No. 6,207,085; 6,252,167 & 7,348,484

Box Guard™

Fire-rated pad for electrical boxes

Code	Description	Qty.
66366	Single box	50
66367	Double box	50
66369	4-11/16" x 4-11/16"	50



FEATURES

- Adheres to back of electrical box
- Non-conductive
- Highly intumescent
- STC rating 53

Application • One component fire-rated for use in electrical boxes • It is inserted on the inside back wall of an electrical box prior to wiring



US Patent No. 6,207,085 & 6,252,167

Putty Sticks & Pads

Fire-rated putty

Code	Description	Qty.
66345	18 cu./in. - stick	12
66340	6" x 7" x 1/8" thick	20
66335	7" x 7" x 1/8" thick	20



FEATURES

- Applied by hand
- No asbestos fillers
- Pads - STC rating 60
- For interior use
- Adheres to all common building surfaces

Application • Putty sticks are used to seal around penetrating items through fire-rated walls, floors and within blank openings • Putty pads are used to maintain the hourly rating of fire-rated walls containing electrical outlet boxes and to reduce sound transmission • Hand moldable with no curing time





METACAULK® FIRESTOP PRODUCTS

Continued

Wire Pulling Tools

Wire Pulling Devices

Composite Sheet

For large openings with penetrating items

Code	Description	Qty.
66320	36" x 36"	1



FEATURES

- Light weight
- Thinner sheets
- Re-enterable
- No VOC

Application • Rigid fire resistive panel used to seal penetrations and restore the fire rating to floor/ceilings or walls • Made of reinforced, highly intumescent material bonded on one side to a galvanized steel sheet

- Ideal for clean room applications



US Patent No. 6,207,085

Firestop Pillows

For large temporary openings

Code	Description	Qty.
66362	2" x 9" x 6"	10
66363	3" x 9" x 6"	10



FEATURES

- Forms a very strong char
- No wire mesh required
- Easy to install - no tools

Application • Intumescent • Designed for use primarily in large temporary or frequently accessed openings with cables, cable trays, blank openings or multiple penetrations



Firestopping

Pipe Joining

Fire-Rated Mortar

For large openings

Code	Description	Qty.
66331	20 lbs. pail	1
66334	45 lbs. bag	1



FEATURES

- Non-sag adjustable consistency
- High yield per lb.
- No special tools needed

Application • Rapid hardening gypsum/cement compound for large openings

- Sets without shrinking and can form a rigid, gas tight, fire resistant seal
- Can be cut or drilled and resealed

Recommended for

- Power cables • Fiber optic
- Telephone cables • Aluminium or steel cable trays • EMT
- Copper • Steel • Cast iron pipe



Other Products

Industrial Cable Coating

Code	Description	Qty.
50250	5 gal.	1



FEATURES

- No cable derating
- Interior & exterior use
- Easy to apply
- VOC compliant

For power cables

Application • Water-based heavy duty spray coating designed to prevent vertical and horizontal spread of fire along grouped or single communication or power cables

- Compatible with and adheres to typical cable jacketing materials



Joint Strip

Flexible material for up to 1" wide joints

Code	Description	Qty.
66700	1/16" x 1" x 82' strip	6
66701	1/16" x 1-1/2" x 82' strip	4
66704	1/16" x 2" x 82' strip	3
66702	1/16" x 2-1/2" x 82' strip	2
66703	1/16" x 3" x 82' strip	2
66705	1/16" x 4" x 82' strip	2



FEATURES

- No firestop caulk required
- Single sided application
- Simple & easy to use



Application • Flexible strip firestop material used in concrete and masonry floor and wall joints up to 1" wide

- Prevents the passage of fire between joints

Recommended for

- Stadium construction, tilt up panels
- Curtain wall panels
- All concrete and masonry wall and floor construction joint applications

US Patent No. 6,207,085



Wrap Strip

Flexible intumescent strip for plastic and insulated pipe

Code	Description	Qty.
66135	1" x 12'	6
66136	2" x 12'	4



FEATURES

- No cure time
- Easy to apply
- Long length means less waste
- Systems up to 14" PVC
- Highly intumescent



Application • Simply wrap required number of strips around penetrating item to completely fill the annular space or as required by system design

- When exposed to heat, expands to form a hard char to seal off the penetration

Recommended for

- Plastic and insulated pipe applications

US Patent No. 6,207,085



*FBC™ System Compatible™ indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings.

**FBC™, FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of the Lubrizol Corporation.

Sound Transmission Class (STC) rating - Tested in a UL 411 wall assembly/section to ASTM E90

METACAULK® APPLICATION CHART

Wire Pulling Tools

Wire Pulling Devices

Firestopping

Pipe Joining

Other Products

PIPE APPLICATION											
Application	1000	MC 150+	350i	835+	Pass Thru	Pipe Collar	Intumescent Sleeve	Putty	Mortar	Wrap Strip	Joint Strip
Metal Pipe - EMT, Copper	●	●	●	●				●	●		
Multiple Metal	●	●	●	●					●		
Insulated Metal Pipe	●	●	●	●						●	
Open Plastic Pipe - 2" & smaller	●	●	●			●	●			●	
Open Plastic Pipe - up to 4"						●	●			●	●
Closed Plastic Pipe - 4" & smaller	●					●	●			●	
Open/Closed Plastic Pipe - 6"						●	●			●	
Open/Closed Plastic Pipe - 8"							●			●	
Glass Pipe				●					●		

CABLE APPLICATION									
Application	1000	MC 150+	350i	835+	Pass Thru	Putty	Composite Sheet	Pillows	Mortar
Single or Bundled Cables	●	●	●	●	●	●		●	●
Cable Trays							●	●	●

CONSTRUCTION APPLICATION								
Application	1000	MC 150+	835+	Putty	Composite Sheet	Pillows	Mortar	Joint Strip
Construction Joints	●		●					●
Top of Wall	●		●					●
Large Openings					●	●	●	
Blank Openings		●	●	●	●	●	●	


ELECTRICAL APPLICATION				
Application	Box Guard™	Cover Guard™	Putty Pads	Joint Strip
Electrical Outlet Boxes	●	●	●	
24" x 24" Steel Utility Box				●

Pipe Joining

Low-VOC Solvent Cements •

Primer & Cleaner •

Pipe Thread Sealants •





RECTORSEAL® LOW-VOC SOLVENT CEMENTS

Wire Pulling Tools

Wire Pulling Devices

PVC Electrical Conduit 633L

○ Clear/Gray - medium body solvent cement

Code	Description	Qty.
55980	½ pt. - clear	24
55983	1 pt. - clear	12
55985	1 qt. - clear	12
55986	1 gal. - clear	4
55995	1 pt. - gray	12
55996	1 qt. - gray	12



PW-GDW-SW



FILE NO. 1796

Clear Only

FEATURES

- Conduit types I & II
- LEED compliant
- 2 year shelf life
- Meets ASTM D2564 specs

Application • Clear or gray to match conduit color • Thick formula to reduce runoff • Up to and including 6" schedule 40 and schedule 80

Recommended for

- PVC conduit



Arctic™ 616L

○ Clear - medium body PVC solvent cement

Code	Description	Qty.
55909	½ pt.	24
55919	1 pt.	12
55948	1 qt.	12
55953	1 gal.	4



PW-GDW-SW



FILE NO. 1796

FEATURES

- Formulated for use in cold weather
- LEED compliant
- NSF approved for potable water
- 2 year shelf life
- Exceeds ASTM D2564 specs

Application • Premium polyvinyl chloride (PVC) solvent cement used for joining PVC pipe and socket-type fittings which meet Class 12454 as defined in ASTM specification D1784 • Pipe up to 6" schedule 40; 1-¼" schedule 80 • Remains stable from 0°F to 120°F

Recommended for

- Potable water • Pressure pipe
- Gas • Conduit • Sewers
- DWV systems

Also available in gal. can



Gene™ 404L

○ Clear - regular body PVC solvent cement

Code	Description	Qty.
55901	¼ pt.	24
55902	½ pt.	24
55904	1 pt.	12
55906	1 qt.	12
55908	1 gal.	4



PW-GDW-SW



FILE NO. 1796

FEATURES

- Fast setting formula
- LEED compliant
- NSF approved for potable water
- 2 year shelf life
- Exceeds ASTM D2564 & D3138 specs

Application • Polyvinyl chloride (PVC) solvent cement used for joining PVC pipe and socket-type fittings which meet Class 12454 as defined in ASTM specification D1784 • ABS to PVC non-pressured transition joints • Schedule 40 up to 2" pressure; up to 4" non-pressure pipe (DWV)

Recommended for

- Potable water
- Pressure pipe • Gas
- Conduit • Sewers
- DWV systems



Firestopping

Pipe Joining

Other Products

Gold™ 844L

○ Clear - heavy body PVC solvent cement

Code	Description	Qty.
55950	¼ pt.	24
55951	½ pt.	24
55952	1 pt.	12
55954	1 qt.	12
55955	1 gal.	4



PVC-DWV-SW



FILE NO. 1796

FEATURES

- Excellent gap filling
- LEED compliant
- NSF approved for potable water
- 2 year shelf life
- Exceeds ASTM D2564 specs

Application • Polyvinyl chloride (PVC) solvent cement used for joining PVC pipe and socket-type fittings which meet Class 12454 as defined in ASTM specification D1784

- For pipe up to 12" schedule 40 and schedule 80

Recommended for

- Potable water
- Pressure pipe • Gas
- Conduit • Sewers
- DWV systems



Hot™ 203L

● Blue - medium body PVC solvent cement

Code	Description	Qty.
55988	¼ pt.	24
55989	½ pt.	24
55990	1 pt.	12
55993	1 qt.	12
55994	1 gal.	4



PVC-DWV-SW



FILE NO. 1796

FEATURES

- Fast drying
- Excellent in cold weather
- LEED compliant
- 2 year shelf life
- Meets ASTM D2564 specs

Application • Polyvinyl chloride (PVC) solvent cement joins both rigid and flexible PVC pipe and socket-type fittings which meet Class 1245 as defined in ASTM specifications D1784 • For all rigid PVC classes up to 6" schedule 40 and 1-¼" schedule 80

Recommended for

- Irrigation • Pools
- Spas • Potable water
- Pressure pipe • Gas
- Conduit • Sewers
- DWV systems • ENT
- Flexible PVC hose



Also available in gal. can

Homer™ 828L

○ Gray - heavy body PVC solvent cement

Code	Description	Qty.
55960	½ pt.	24
55961	1 pt.	12
55963	1 qt.	12
55964	1 gal.	4



PVC-DWV-SW



FILE NO. 1796

FEATURES

- Superior bonding strength
- LEED compliant
- NSF approved for potable water
- 2 year shelf life
- Exceeds ASTM D2564 specs

Application • Polyvinyl chloride (PVC) solvent cement used for joining PVC pipe and socket-type fittings which meet Class 12454 as defined in ASTM specification D1784 • For pipe up to 12" schedule 40 and schedule 80

- Remains stable from 0°F to 120°F

Recommended for

- Potable water
- Pressure pipe
- Gas • Conduit
- Sewers
- DWV systems



Also available in gal. can



RECTORSEAL® LOW-VOC PRIMERS & CLEANERS

Wire Pulling Tools

Wire Pulling Devices

Firestopping


Pipe Joining

Other Products

Jim™ PR-1L

○ Purple - hi-etch primer

Code	Description	Qty.
55910	¼ pt.	24
55912	½ pt.	24
55914	1 pt.	12
55918	1 qt.	12
55920	1 gal.	4



FEATURES

- Fast acting
- Superior bonding
- LEED compliant
- 2 year shelf life
- Low-VOC
- Meets ASTM F656 specs

Application • Prepares surfaces for superior bonding strength • For use on PVC and CPVC pipe, tubing and socket-type fittings in both schedule 40 and schedule 80

Recommended for

- Potable water • Pressure pipe
- Gas • Conduit • Sewers
- DWV systems



Sam™ CL-3L

○ Clear - cleaner

Code	Description	Qty.
55929	¼ pt.	24
55930	½ pt.	24
55932	1 pt.	12
55934	1 qt.	12
55936	1 gal.	4



FEATURES

- Fast acting
- Safe for potable water
- LEED compliant
- 2 year shelf life
- Low-VOC

Application • Clear cleaner for dissolving grease and dirt to prepare bonding surfaces for solvent cementing • Use for PVC, CPVC and ABS pipe, tubing and socket-type fittings schedule 40 and schedule 80

Recommended for

- Potable water
- Pressure pipe • Gas • Conduit
- DWV systems





RECTORSEAL® PIPE THREAD SEALANTS

RectorSeal No. 5®

Multi-purpose pipe thread sealant

Code	Description	Qty.
25790	1-¾ oz.	24
25631	¼ pt.	24
25551	½ pt.	24
25431	1 pt.	12
25300	1 qt.	12
25271	1 gal.	4
25191	5 gal.	1
25112	55 gal.	1



FEATURES

- Soft set / Slow drying
- Lead free
- Smooth application
- 2 year shelf life
- Certified to NSF/ANSI 61-G

Application • Lubricates and protects threaded pipe and fittings • Can be pressurized immediately up to 100 psi for piping up to 2" diameter • Ideal for a wide variety of fluids and gases including potable water

Recommended for

- Galvanized Steel
- Iron • Brass
- Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC



Also available in 55 gal. container.

RectorSeal T plus 2®

PTFE enriched pipe thread sealant

Code	Description	Qty.
23710	1-¾ oz.	24
23631	¼ pt.	24
23551	½ pt.	24
23431	1 pt.	12
23391	1 qt.	12
23271	1 gal.	4
23191	5 gal.	1
23112	55 gal.	1



FEATURES

- Non-setting
- Lead free
- 2 year shelf life
- Certified to NSF/ANSI 61-G

Application • Contains PTFE & synthetic fibers for superior performance • Can be pressurized immediately following application

Recommended for

- Galvanized Steel • Iron
- Brass • Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC
- CPVC • ABS



Also available in 55 gal. container.

RECTORSEAL® PIPE THREAD SEALANTS

Continued

Wire Pulling Tools

Wire Pulling Devices

Firestopping

Pipe Joining

Other Products

RectorSeal Tru-Blu™

Vibration resistant pipe thread sealant

Code	Description	Qty.
31780	1-¾ oz.	24
31631	¼ pt.	24
31551	½ pt.	24
31431	1 pt.	12
31300	1 qt.	12



Certified to NSF/ANSI 61-G



FILE NO. 1282

FEATURES

- Fast drying / Flexible set
- Contains PTFE
- Lead free
- 2 year shelf life
- Certified to NSF/ANSI 61-G

Application • For high vibration environments such as refrigeration and industrial applications • Designed for sealing vibration prone NPT connections

Recommended for

- Galvanized Steel • Iron
- Brass • Copper • Aluminum
- Stainless Steel • PVC
- Polyethylene
- Reinforced fiberglass



No. 5® Sub-Zero

Low temperature, low odor pipe thread sealant

Code	Description	Qty.
27731	¼ pt.	24
27651	½ pt.	24
27541	1 pt.	12
27460	1 qt.	12
27371	1 gal.	4
27111	5 gal.	1
27222	55 gal.	1



FILE NO. 1282

FEATURES

- Low temperature application -35°F
- All weather formula
- Lead free

Application • Odorless, non-staining, low temperature application • Brushable to -35°F • Can be pressurized immediately

Recommended for

- Galvanized Steel
- Iron • Brass • Copper • Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC



See ordering chart for container sizes available.

Other Products

Duct Seal •

Cutting Oils •

Anti-Seize Compound •

Specialty Sealant Caulks •

Specialty Cleaners & Degreasers •



OTHER PRODUCTS

RectorSeal® Duct Seal

Gray putty compound

Code	Description	Qty.
81880	1 lb.	10
81881	5 lbs.	2



FEATURES

- Asbestos free
- Air / water tight seal
- Resistant to water, alcohols, mild acids & bases
- Non-corrosive / non-irritant
- Paintable

Application • Permanently soft, non-toxic, putty-type compound which adheres to most clean, dry surfaces

- Can be hand applied from 25°F to 120°F

Recommended for

- Sealing around the ends of electrical conduits and boxes
- Flashings
- Service mast entries



Dark Cutting Oil

Low rpm machine thread cutting oil

Code	Description	Qty.
94392	1 qt.	12
94272	1 gal.	6
94192	5 gal.	1
94111	55 gal.	1

FEATURES

- Increased lubricity/longer die life
- Penetrates quickly
- Keeps dies cool

Application • Designed to reduce friction

- Effective coolant and anti-weld agent
- An extreme pressure lubricant during thread cutting operations
- Will not congeal above 20°F



Light Cutting Oil

High rpm machine thread cutting oil

Code	Description	Qty.
93392	1 qt.	12
93272	1 gal.	6
93192	5 gal.	1
93111	55 gal.	1

FEATURES

- Increased lubricity/longer die life
- Penetrates quickly
- Keeps dies cool

Application • Designed to reduce friction

- Effective coolant and anti-weld agent
- An extreme pressure lubricant during thread cutting operations
- Will not congeal above 20°F



Copper-Rich™

High temperature anti-seize and lubricant

Code	Description	Qty.
72851	8 oz.	12
72841	1 lb.	12

FEATURES

- Highly conductive
- Exceeds military spec MIL-A-907E

Application • Pure micro-sized copper flakes dispersed in a non-melt, high temperature grease

- Resists seizure
- Color: copper

Recommended for

- All metal connections including stainless steel to 1800°F
- Ideal for use where electrical conductivity is important



SPECIALTY SEALANT CAULKS

RectorSeal® RS 136

Fire block / smoke seal caulk

Code	Description	Qty.
66408	10.3 oz. cartridge	12



FEATURES

- Easy application
- Interior applications
- Water Clean-up
- ASTM E 136 compliant

Application • General purpose, residential acoustical fireblock

Recommended for

- Electrical • Plumbing • Plastic pipe
- Telephone communication systems penetrations



RectorSeal® Silicone Sealant

General purpose

Code	Description	Qty.
57505	10.3 oz. tube - white	12
57506	10.3 oz. tube - clear	12

FEATURES

- Remains flexible
- Vibration resistant
- Indoors/outdoor

Application • Ideal for general sealing

- Dries to touch in 30 minutes and fully cures in 24 hours

Recommended for

- Around electrical panels • Windows • Doors
- Pipes/vents • Corner joints • Aluminum siding
- Other interior / exterior building materials



RectorSeal® Hi-Temp™

100% RTV silicone caulk

Code	Description	Qty.
57500	10.1 oz. cartridge	24

FEATURES

- One component
- USDA specs for use in federally inspected meat and poultry plants
- F.D.A. reg #21 CFR 177.2600
- TT-S-001543A (COM-NBS) Class A
- TT-S00230C (COM-NBS) Class AA
- MIL-A-46106B Amend 3, Type 1
- Canadian 19-GP-9MA, Type 1

Application • Cures to a strong durable resilient rubber

Recommended for • Glass • Clean metal • Most types of non-oily wood • Vulcanized silicone rubber • Silicone resins

- Natural and synthetic fiber • Ceramic • Paper
- Many painted and plastic surfaces



Wire Pulling Tools

Wire Pulling Devices

Firestopping

Pipe Joining

Other Products

SPECIALTY CLEANERS

Zipp™ Quick drying degreaser

Code	Description	Qty.
82642	14 oz. aerosol	12

FEATURES

- Cleaner / degreaser
- Leaves no residue
- Non-flammable
- Non-conductive

Application • Quick drying, safety solvent degreaser that instantly removes grease, oil, waxes, tar, gums, grime, dirt, carbon, greasy stains, bilge slime and similar soils from most hard surfaces • Will not short out electrical equipment

- Recommended for use** • Oil burner parts
 • Compressors • Refrigeration units
 • Greasy fan blades • Strainers • Engines
 • Stoves • Relay contact points
 • Electrical equipment



Zipp™ II Environmentally safer, quick drying degreaser

Code	Description	Qty.
82645	12 oz. aerosol	12

FEATURES

- Cleaner / degreaser
- Leaves no residue
- Non-flammable
- Non-conductive
- Non-chlorinated

Application • Quick drying, safety solvent degreaser that instantly removes grease, oil, waxes, tar, gums, grime, dirt, carbon, greasy stains, bilge slime and similar soils from most hard surfaces • Will not short out electrical equipment • Contains no carbon tet or restricted solvents

- Recommended for use** • Oil burner parts
 • Compressors • Refrigeration units
 • Greasy fan blades • Strainers • Engines
 • Stoves • Relay contact points
 • Electrical equipment



Grime-Solv™ Foaming, heavy duty cleaner and degreaser

Code	Description	Qty.
88436	14 oz. aerosol	12

FEATURES

- Safe for metals
- Wipes clean or rinses with water
- Non-flammable
- Non-corrosive

Application • Lifts encrusted grime, grease or carbon • Use to remove stains from concrete driveways and brick walls, to clean white wall tires and for cleaning surfaces before painting

- Recommended for** • Oil burning • A/C and refrigeration equipment • Marine and automotive engines • Machinery that can be rinsed with water or wiped with a rag



MISCELLANEOUS

Draft-Block™

Expanding polyurethane foam

Code	Description	Qty.
96500	12 oz. aerosol	12

FEATURES

- Expands 3X
- Tack-free in approx. 45 min.
- No ureaformaldehyde

Application • Excellent filler which bonds and insulates
 • Fill voids, cracks, crevices and small cavities on flat or irregular surfaces
 • Reduces sound transmission
 • Totally dielectric



Lets-Go™

Penetrant, lubricant and freeze-up preventer

Code	Description	Qty.
73012	12 oz. aerosol	12

FEATURES

- Loosens frozen bolts, nuts & joints
- Protects from water & weather

Application • Covers metal surfaces with a clinging, tough, long-lasting film of lubricant
 • The wetting power acts quickly on rusted and seized parts
 • Displaces moisture from wiring and equipment.



Cold Galvanizing Spray

Protection of hot-dip galvanizing

Code	Description	Qty.
86625	16 oz. aerosol	12

FEATURES

- Stops rust and corrosion
- Indoors or outdoors

Application • Contains 95% pure zinc and forms a tough, durable and flexible zinc metal coating that bonds electrochemically with the base metal to protect against rust and corrosion
 • To prevent and retard rust and corrosion on welded joints, fencing, storage tanks, pipe lines, metal buildings, marine and other similar applications



MISCELLANEOUS

Wire Pulling Tools

Wire Pulling Devices

RectorSeal® EP-200

Epoxy putty

Code	Description	Qty.
97600	2 oz.	24
97601	2 oz. refill	24
97602	Blistercard	12
97606	EP-400 4 oz.	12



FEATURES

- Mixes like putty
- Hardens in minutes
- Can be drilled, taped, filed, machined, sanded and painted
- Bonds and fills a variety of materials

Application • Pre-measured, high-grade epoxy and hardener formulated together in one stick
 • Break off the amount needed for each repair • Bonds to most surfaces



Firestopping

GOJO®*

Hand cleaner

Code	Description	Qty.
40500	Original 14 oz. tub	12
40507	Natural orange 14 oz.	12

FEATURES

- Safe to use
- Non-toxic
- Biodegradable

Application • Thoroughly and safely cleans adhesives, asphalt, tar and paint

*GOJO is a registered trademark of GOJO Industries



Pipe Joining

Buz-Awf™

Wasp and hornet spray

Code	Description	Qty.
84390	16 oz. aerosol	12

FEATURES

- High pressure spray
- Shoots 20 ft stream
- Non-conductive up to 47KV

Application • Kills wasps, hornets, yellow jackets and bees • E.P.A. REG. NO. 3862-174-51219, E.P.A. EST. NO. 9143-TX-1



Other Products

PRODUCT CODE INDEX

CODE	PAGE												
23112	31	55948	28	66353	22	88436	36	97958	13	98143	17	98152	20
23191	31	55950	29	66354	22	93111	34	97961	14	98144	17	98153	21
23271	31	55951	29	66362	24	93192	34	97962	14	98145	17	98154	21
23391	31	55952	29	66363	24	93272	34	97963	14	98146	17	98155	21
23431	31	55953	28	66366	23	93392	34	97964	14	98147	17	98156	21
23551	31	55954	29	66367	23	94111	34	97965	14	98148	17	98157	21
23631	31	55955	29	66369	23	94192	34	97966	14	98149	17	98158	21
23710	31	55960	29	66383	21	94272	34	97967	14	98150	17	98159	21
25112	31	55961	29	66385	21	94392	34	97968	14	98151	17	98160	21
25191	31	55963	29	66389	21	96500	37	97969	14	98152	17	98161	21
25271	31	55964	29	66408	35	97100	6	97970	14	98153	17	98162	21
25300	31	55980	28	66582	22	97103	7	97971	14	98154	17	98163	21
25431	31	55983	28	66584	22	97105	10	97972	14	98155	17	98164	21
25551	31	55985	28	66611	21	97106	10	97973	14	98156	17	98165	22
25631	31	55986	28	66613	21	97108	10	97974	14	98157	17	98166	22
25790	31	55988	29	66616	21	97113	8	97975	14	98158	17	98167	22
27111	32	55989	29	66640	20	97114	11	97976	14	98159	17	98168	22
27222	32	55990	29	66645	21	97115	8	97977	14	98160	17	98169	22
27371	32	55993	29	66648	21	97116	11	97978	14	98161	17	98170	22
27460	32	55994	29	66700	25	97117	8	97979	14	98162	17	98171	22
27541	32	55995	28	66701	25	97118	11	97980	14	98163	17	98172	22
27651	32	55996	28	66702	25	97119	8	97998	13	98164	17	98173	22
27731	32	57500	35	66703	25	97119	9	98117	16	98165	17	98174	22
31300	32	57505	35	66704	25	97120	11	98118	16	98166	17	98175	22
31431	32	57506	35	66705	25	97121	11	98119	16	98167	17	98176	22
31551	32	66019	21	66740	22	97122	11	98120	16	98168	17	98177	23
31631	32	66135	25	66743	22	97123	11	98121	16	98169	17	98178	23
31780	32	66136	25	66746	22	97125	11	98122	16	98170	17	98179	23
40500	38	66265	23	66749	22	97127	11	98123	16	98171	17	98180	23
40507	38	66266	23	66752	22	97128	11	98124	16	98172	17	98181	23
50250	25	66270	23	66755	22	97129	11	98125	16	98173	18	98182	23
55901	28	66272	23	66758	22	97131	11	98126	16	98174	18	98183	23
55902	28	66274	23	66761	22	97140	9	98127	16	98175	18	98184	23
55904	28	66276	23	66764	22	97143	9	98128	16	98176	18	98185	23
55906	28	66303	20	66767	22	97145	9	98129	16	98177	18	98186	23
55908	28	66305	20	66770	22	97148	11	98130	16	98178	18	98187	23
55909	28	66307	20	66773	22	97150	11	98131	16	98179	18	98188	23
55910	30	66309	20	66776	22	97153	11	98132	16	98180	18		
55912	30	66312	20	66779	22	97600	38	98133	16	98181	18		
55914	30	66320	24	72841	34	97601	38	98134	16	98182	18		
55918	30	66331	24	72851	34	97602	38	98135	16	98183	18		
55919	28	66334	24	73012	37	97606	38	98136	16	98184	18		
55920	30	66335	23	81880	34	97924	14	98137	16	98185	18		
55929	30	66340	23	81881	34	97929	14	98138	16	98186	18		
55930	30	66345	23	82642	36	97932	14	98139	16	98187	18		
55932	30	66350	22	82645	36	97935	14	98140	16	98188	18		
55934	30	66351	22	84390	38	97948	13	98141	17	98150	20		
55936	30	66352	22	86625	37	97949	13	98142	17	98151	20		


Wire Pulling Tools

Wire Pulling Devices

Frestopping

Pipe Joining

Other Products



Through the use of current technology and social media, RectorSeal provides up-to-date technical information and marketing materials.

Company Homepage:

An online hub of readily available resources for our full-line of specialty chemicals and tools including: product codes, MSDS and product data sheets. Promotional literature and artwork can be easily viewed. Trade show scheduling and booth information are also updated frequently.

Social Media:

Up to the minute information from RectorSeal regarding new products, press releases, market trends and trade articles are sent directly to your wall, time-line and mobile devices.

Online Video:

Watch instructional videos on how to effectively and properly use RectorSeal products. Subscribe to our channel and receive new product videos instantly.

Online Training:

Earn certifications from RectorSeal for approved field use of our specialty products. Lessons and exams can be completed at your own pace and results accessed from your personal computer.



To utilize these services, visit www.rectorseal.com

Contact: RectorSeal®

2601 Spenwick Drive, Houston, TX 77055

P 713-263-8001 | 800-231-3345

F 713-263-7577 | 800-441-0051

W www.rectorseal.com

Distributed by: