



Milwaukee®

Nothing but **HEAVY DUTY**.®



2016
**FEDERAL GOVERNMENT
SPOTLIGHT**

*Milwaukee® Delivers Performance and Productivity
for the Government of Canada*

Hand Tools Standing Offer # E60HP-16TOOL/001/HP

**ACKLANDS
GRAINGER®**

INDUSTRIAL • SAFETY • FASTENERS



**THE WORLD LEADER
IN CORDLESS INNOVATION**

M12
SYSTEM

M18
SYSTEM



OVER 160 JOBSITE SOLUTIONS

GAME-CHANGING SOLUTIONS

At Milwaukee®, the phrase “good enough” doesn’t exist in our vocabulary. Our goal is to solve problems in ways that have never been done before. The result: tools that offer unmatched levels of performance, productivity and life.



BUILT ON THE BEST FOUNDATION



REDLITHIUM™ BATTERIES

They last longer, think faster and work harder than all other professional LITHIUM-ION batteries. Built to withstand even the harshest environments, REDLITHIUM™ batteries deliver more work over the life of the battery, no matter what the job.



MILWAUKEE® HIGH PERFORMANCE MOTORS

Highly advanced motor technology boosts efficiency, generating more power from a compact power plant. That means the ultimate performance, durability and run-time comes in a smaller, lighter package.



REDLINK™ INTELLIGENCE


An advanced combination of hardware and software, REDLINK™ Intelligence enables full-circle communication between our batteries and tools, allowing for unmatched levels of performance, protection and productivity.

NEW!

ONE-KEY™

UNLOCKING THE DIGITAL JOBSITE.™

ONE-KEY™, the first digital platform for jobsite tools. By integrating industry-leading tool electronics with a custom-built cloud based program, ONE-KEY™ will provide a new level of control and access to information that will revolutionize the way work gets done. This will fundamentally change the way users interact with their tools, and help solve user problems and frustrations the industry has never before been able to address.



**SMART
TOOLS**



**SYNC
WIRELESSLY**



**ONLINE + MOBILE
RECORD KEEPING**

DIGITAL PLATFORM FOR TOOLS & EQUIPMENT

TOOL CONTROL • INVENTORY MANAGEMENT • TOOL REPORTING

SEE PAGE 11 FOR **NEW ONE-KEY ENABLED CRIMPERS**

GET STARTED:

DOWNLOAD FREE APP NOW!



CREATE AN ACCOUNT ONLINE

[ACCOUNTS.MILWAUKEETOOL.CA](https://accounts.milwaukeetool.ca)

Milwaukee®

POWER TOOLS



M18 FUEL™ **M12**

M18 FUEL

1/2" Drill/Driver Kit

MTL2703-22
Bare Tool: MTL2703-20

Specifications:

| | |
|-------------|--|
| Peak Torque | 1,200 in-lbs |
| RPM | 0 – 550 / 0 – 2,000 |
| Chuck type | 1/2" Metal Single Sleeve – Ratcheting Lock |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Hammer Drill/Driver Kit

MTL2607-22

Specifications:

| | |
|-------------|---------------------|
| Peak Torque | 525 in-lbs |
| RPM | 0 – 450 / 0 – 1,800 |
| BPM | 0 – 28,800 |

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case

M18 FUEL

1/2" Hammer Drill/Driver Kit

MTL2704-22
Bare Tool: MTL2704-20

Specifications:

| | |
|-------------|---------------------|
| Peak Torque | 1,200 in-lbs |
| RPM | 0 – 550 / 0 – 2,000 |
| BPM | 0 – 32,000 |

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Compact Drill/Driver Kit

MTL2606-22ct

Bare Tool: MTL2606-20

Specifications:

| | |
|-------------|--------------------------|
| Peak Torque | 500 in-lbs |
| RPM | 0 – 450 / 0 – 1,800 |
| Chuck Type | 1/2" Metal Single Sleeve |

Includes: (2) M18™ REDLITHIUM™ Compact Battery Packs, Multi-Voltage Charger, Carrying Case

M18 FUEL

2-Tool Combo Kit

MTL2897-22

Includes: (1) M18 FUEL™ 1/2" Hammer Drill/Driver (Bare Tool), (1) M18 FUEL™ 1/4" Hex Impact Driver (Bare Tool), (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ & M12™ Multi-Voltage Charger, (2) Belt Clip, (2) Bit Holder, (1) Side Handle, (1) Carrying Case



M18™ 1/4" 2-Speed Impact Driver Kit

MTL2657-22

Bare Tool: MTL2657-20

Specifications:

| | |
|------------------|--------------|
| Fastening Torque | 1,500 in-lbs |
| IPM | 0 – 3,450 |
| RPM | 0 – 2,750 |

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL

HOLE HAWG® Right Angle Drill Kit w/ QUIK-LOK™

MTL2708-22
Bare Tool: MTL2708-20

Specifications:

| | |
|------------|--|
| RPM | 0 – 1,200 |
| Chuck Type | 7/16" Hex QUIK-LOK™ |
| Capacity | For Augers up to 1-1/4"; Self-Feed Bits up to 2" |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18 FUEL

1/4" Hex Impact Driver Kit

MTL2753-22
Bare Tool: MTL2753-20

Specifications:

| | |
|------------------|--------------|
| Fastening Torque | 1,800 in-lbs |
| IPM | 0 – 3,700 |
| RPM | 0 – 3,000 |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



M18 FUEL

HOLE HAWG® 1/2" Right Angle Drill Kit

MTL2707-22
Bare Tool: MTL2707-20

Specifications:

| | |
|------------|--|
| RPM | 0 – 1,200 |
| Chuck Type | 1/2" Metal |
| Capacity | For Augers up to 1-1/4"; Self-Feed Bits up to 2" |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ Cordless LITHIUM-ION 2-Tool Combo Kit

MTL2691-22

Includes: (1) M18™ Compact 1/2" Drill Driver (Bare Tool), (1) M18™ 1/4" Hex Impact Driver, (2) M18™ Compact REDLITHIUM™ Battery, (1) M18™ & M12™ Multi-Voltage Charger, (1) Contractor Bag



M18™ Cordless LITHIUM-ION 2-Tool Combo Kit

MTL2697-22

Includes: (1) M18™ Compact 1/2" Hammer Drill/Driver (Bare Tool), (1) M18™ 1/4" Hex Impact Driver (Bare Tool), (2) M18™ REDLITHIUM™ XC Extended Capacity Battery, (1) M18™ & M12™ Multi-Voltage Charger, (1) Contractor Bag



1/2" Hammer Drill with Carrying Case

MTL5380-21

Specifications:

| | |
|------|-------------------------|
| RPM | 0 – 1,500 / 0 – 3,500 |
| BPM | 0 – 24,000 / 0 – 56,000 |
| Amps | 9 |



Includes: (1) Carrying Case, (1) Chuck Key, (1) Side Handle

1/2" Magnum® Drill

MTL0299-20

Specifications:

| | |
|------------|------------------|
| RPM | 0 – 850 |
| Amps | 8 |
| Chuck Type | Heavy-Duty Keyed |

Includes: (1) Chuck Key with Holder, (1) Side Handle



M18 FUEL

1/2" High Torque Impact Wrench w/ Friction Ring Kit

MTL2763-22

Bare Tool: MTL2763-20

Specifications:

| | |
|--------------------------------|------------------|
| Max Fastening Torque (2-Modes) | 100 / 700 ft-lbs |
| Nut-Busting Torque | 1,100 ft-lbs |
| IPM | 0 – 2,300 |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M12 FUEL

1/2" Hammer Drill/Driver Kit

MTL2404-22

Bare Tool: MTL2404-20

Specifications:

| | |
|-------------|---------------------|
| Peak Torque | 350 in-lbs |
| RPM | 0 – 450 / 0 – 1,700 |
| BPM | 0 – 25,500 |

Includes: (1) M12™ REDLITHIUM™ XC 4.0 Extended Capacity Battery Pack, (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, Belt Clip, Charger, Carrying Case



M18 FUEL

3/4" High Torque Impact Wrench w/ Friction Ring Kit

MTL2764-22

Bare Tool: MTL2764-20

Specifications:

| | |
|--------------------------------|------------------|
| Max Fastening Torque (2-Modes) | 375 / 750 ft-lbs |
| Nut-Busting Torque | 1,200 ft-lbs |
| IPM | 0 – 2,300 |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M12 FUEL

1/2" Drill/Driver Kit

MTL2403-22

Bare Tool: MTL2403-20

Specifications:

| | |
|-------------|--------------------------|
| Peak Torque | 350 in-lbs |
| RPM | 0 – 450 / 0 – 1,700 |
| Chuck Type | 1/2" Metal Single Sleeve |

Includes: (1) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, Belt Clip, Charger, Carrying Case



M18™ Right Angle Impact Wrench Kit

MTL2668-22

Bare Tool: MTL2668-20

Specifications:

| | |
|----------------------------|-----------------------|
| Fastening Torque (2-Modes) | 30 / 60 ft-lbs |
| IPM | 0 – 2,400 / 0 – 3,400 |
| RPM | 0 – 1,500 / 0 – 2,250 |

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M12™ 3/8" Drill/Driver Kit

MTL2407-22

Bare Tool: MTL2407-20

Specifications:

| | |
|-------------|--------------------------|
| Peak Torque | 275 in-lbs |
| RPM | 0 – 400 / 0 – 1,500 |
| Chuck Type | 3/8" Metal Single Sleeve |

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



1/2" Impact Wrench with Rocker Switch and Friction Ring Socket Retention

MTL9071-20

Specifications:

| | |
|-------------|------------|
| Peak Torque | 300 ft-lbs |
| RPM | 1,800 |
| IPM | 2,600 |



3/4" Impact Wrench with Rocker Switch and Friction Ring Socket Retention

MTL9075-20

Specifications:

| | |
|-------------|---------------|
| Peak Torque | 380 ft-lbs |
| RPM | 600 – 1,800 |
| IPM | 1,000 – 1,800 |



M12 FUEL

1/4" Hex Impact Driver Kit

MTL2453-22

Bare Tool: MTL2453-20

Specifications:

| | |
|----------------------------|-----------------------|
| Fastening Torque (2-Modes) | 175 / 1,200 in-lbs |
| IPM | 0 – 3,550 |
| RPM (2-Modes) | 0 – 1,200 / 0 – 2,650 |



Includes: (2) M12™ REDLITHIUM™ 2.0 Compact Battery Packs, Belt Clip, Charger, Carrying Case

M12™ 1/4" Hex Impact Driver Kit

MTL2462-22

Bare Tool: MTL2462-20

Specifications:

| | |
|------------------|--------------|
| Fastening Torque | 1,000 in-lbs |
| IPM | 0 – 3,300 |
| RPM | 0 – 2,500 |



Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case

M12™ 1/4" Ratchet Kit

MTL2456-21

Bare Tool: MTL2456-20

Specifications:

| | |
|------------------|------------------|
| Fastening Torque | 30 ft-lbs |
| RPM | 0 – 250 |
| Anvil | 1/4" Ball Detent |



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Soft Carrying Case

M18 FUEL

SAWZALL® Recip Saw Kit

MTL2720-22

Bare Tool: MTL2720-20

Specifications:

| | |
|---------------|---|
| SPM | 0 – 3,000 |
| Stroke Length | 1-1/8" |
| Blade Clamp | Lever-Action QUIK-LOK™ (Accepts all SAWZALL® Blades) |



Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, (1) Blade, Multi-Voltage Charger, Carrying Case

M18™ SAWZALL® Recip Saw Kit

MTL2621-22

Bare Tool: MTL2621-20

Specifications:

| | |
|---------------|---|
| SPM | 0 – 3,000 |
| Stroke Length | 1-1/8" |
| Blade Clamp | Lever-Action QUIK-LOK™ (Accepts all SAWZALL® Blades) |



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (1) Blade, Multi-Voltage Charger, Carrying Case

M18™ HACKZALL® One-Handed Recip Saw Kit

MTL2625-21

Bare Tool: MTL2625-20

Specifications:

| | |
|---------------|---|
| SPM | 0 – 3,000 |
| Stroke Length | 3/4" |
| Blade Clamp | QUIK-LOK™ (Accepts all SAWZALL® Blades) |



Includes: (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack, (1) Blade, Multi-Voltage Charger, Contractor Bag

M12 FUEL

HACKZALL® Recip Saw Kit

MTL2520-21

Bare Tool: MTL2520-20

Specifications:

| | |
|---------------|-------------------------------|
| SPM | 0 – 3,000 |
| Stroke Length | 5/8" |
| Keyless | QUIK-LOK™ |
| Blade Clamp | (Accepts all SAWZALL® Blades) |



Includes: (1) M12™ REDLITHIUM™ XC 4.0 Extended Capacity Battery Pack, (1) HACKZALL® Blade, Charger, Contractor Bag

13 Amp Orbital Super Sawzall® Recip Saw

MTL6536-21

Specifications:

| | |
|---------------|-------------------------------|
| SPM | 0 – 3,000 |
| Stroke Length | 1-1/4" |
| Keyless | QUIK-LOK™ |
| Blade Clamp | (Accepts all SAWZALL® Blades) |

Includes: Carrying Case



M18 FUEL

Deep Cut Band Saw Kit

MTL2729-22

Bare Tool: MTL2729-20

Specifications:

| | |
|--------------|----------|
| SFPM | 0 – 380 |
| Cut Capacity | 5" x 5" |
| Weight | 15.0 lbs |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case



15 Amp Super Sawzall® Recip Saw

MTL6538-21

Specifications:

| | |
|---------------|-------------------------------|
| SPM | 0 – 2,800 |
| Stroke Length | 1-1/4" |
| Keyless | QUIK-LOK™ |
| Blade Clamp | (Accepts all SAWZALL® Blades) |

Includes: Carrying Case



M18™ Band Saw Kit

MTL2629-22

Bare Tool: MTL2629-20

Specifications:

| | |
|--------------|-----------------|
| SFPM | 480 |
| Cut Capacity | 3-1/4" x 3-1/4" |
| Weight | 10.2 lbs |

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case



M18 FUEL

6-1/2" Circular Saw Kit

MTL2730-22

Bare Tool: MTL2730-20

Specifications:

| | |
|----------------|-------------------------------|
| RPM | 5,000 |
| Bevel Capacity | 50° |
| Cut Capacity | 2-3/16" at 90°; 1-5/8" at 45° |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, (1) Circular Saw Blade, Wrench, Multi-Voltage Charger, Contractor Bag



M18 FUEL

1-1/2" Magnetic Drill Kit

MTL2787-22

Specifications:

| | |
|----------|--|
| Capacity | 1-1/2" Annular Cutter; 1/2" Twist Bit |
| RPM | 400 / 690 |
| Magnet | Operates Without Electricity |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, Multi-Voltage Charger, Carrying Case



M18 FUEL

7-1/4" Circular Saw Kit

MTL2731-22

Bare Tool: MTL2731-20

Specifications:

| | |
|----------------|------------------------------|
| RPM | 5,000 |
| Bevel Capacity | 50° |
| Cut Capacity | 2-1/2" at 90°; 1-7/8" at 45° |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, (1) Circular Saw Blade, Wrench, Multi-Voltage Charger, Contractor Bag



M18™ Metal Cutting Saw Kit

MTL2682-22

Bare Tool: MTL2682-20

Specifications:

| | |
|--------------|-----------|
| RPM | 3,600 |
| Cut Capacity | 1/8" – 2" |
| Blade Size | 5-3/8" |

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (1) 30T METAL TECH™ Carbide-Tipped Blade, Blade Wrench, Multi-Voltage Charger, Contractor Bag



TILT-LOK™ 7-1/4" Circular Saw with Case

MTL6390-21

Specifications:

| | |
|----------------|--|
| RPM | 5,800 |
| Bevel Capacity | 50° |
| Cut Capacity | 2-7/16" at 90°; 1-11/16" at 50°; 1-13/16" at 45° |

Includes: (1) Blade Wrench, (1) Carrying Case, (1) Circular Saw Blade



14" Abrasive Cut-Off Machine

MTL6177-20

Specifications:

| | |
|--------------|----------------|
| RPM | 3,800 |
| Cut Capacity | 4-5/8 X 4-5/8" |
| Amps | 15 |

Includes: (1) Abrasive Wheel, (1) Hex Wrench, (1) Vise



8" Metal Cutting Saw

MTL6370-20

Specifications:

| | |
|--------------|---------|
| RPM | 3,700 |
| Cut Capacity | 2-9/16" |
| Amps | 13 |

Includes: (1) Blade Wrench, (1) Circular Saw Blade



M18 FUEL

4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit

MTL2780-22
Bare Tool: MTL2780-20



Specifications:

| | |
|---------------------|-------|
| RPM | 8,500 |
| Power to Grind | Yes |
| Overload Protection | Yes |

Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case

11 Amp 4-1/2" Small Angle Grinder Paddle, Lock-On

MTL6146-30



Specifications:

| | |
|---------------------|------------|
| Spindle | 5/8" – 11" |
| RPM | 11,000 |
| Overload Protection | Yes |

Includes: Contractor Bag, (1) Flange, (1) Grinding Wheel, (1) Side Handle, (1) Spanner Wrench, (1) Type 27 Guard

15 Amp 7" / 9" Large Angle Grinder

MTL6088-30 with Lock
MTL6088-31 without Lock



Specifications:

| | |
|----------------|------------|
| RPM | 6,000 |
| Wheel Diameter | 7" / 9" |
| Spindle | 5/8" – 11" |

Includes: (1) Flange, (1) Spanner Wrench, (1) Type 27 Guard

13 Amp 5" Small Angle Grinder Trigger Grip

MTL6124-30 with Lock
MTL6124-31 without Lock



Specifications:

| | |
|---------------|------------|
| Spindle | 5/8" – 11" |
| RPM | 9,000 |
| Max Watts Out | 2,100 MWO |

Includes: (1) Flange, (1) Spanner Wrench, (1) Type 27 Guard

11 Amp 5" Small Angle Grinder Trigger Grip AC/DC

MTL6121-31A



Specifications:

| | |
|---------------|------------|
| Spindle | 5/8" – 11" |
| RPM | 11,000 |
| Max Watts Out | 1,400 MWO |

Includes: (1) Flange, (1) Side Handle, (1) Spanner Wrench, (1) Type 27 Guard

13 Amp 6" Small Angle Grinder Paddle

MTL6161-30 with Lock
MTL6161-31 without Lock



Specifications:

| | |
|---------------|------------|
| Spindle | 5/8" – 11" |
| RPM | 9,000 |
| Max Watts Out | 2,100 MWO |

Includes: (1) Flange, (1) Side Handle, (1) Spanner Wrench, (1) Type 27 Guard

11 Amp 4-1/2" Small Angle Grinder Trigger Grip

MTL6121-30 with Lock
MTL6121-31 without Lock



Specifications:

| | |
|---------------|------------|
| Spindle | 5/8" – 11" |
| RPM | 11,000 |
| Max Watts Out | 1,400 MWO |

Includes: (1) Flange, (1) Side Handle, (1) Spanner Wrench, (1) Type 27 Guard

7" Universal Surface Grinding Dust Shroud

MTL49-40-6105



Specifications:

| | |
|----------------------|--------------|
| Length | 10" |
| Diameter | 7" |
| Fits Collar Diameter | 2-1/8" to 3" |

M18 FUEL

1-1/8" SDS Plus Rotary Hammer Kit

MTL2715-22

Bare Tool: MTL2715-20

Specifications:

| | |
|---------------|------------|
| RPM | 0 – 1,350 |
| BPM | 0 – 5,000 |
| Impact Energy | 3.3 ft-lbs |



Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

M12 FUEL

1" SDS Plus Rotary Hammer Kit

MTL2712-22

Bare Tool: MTL2712-20

Specifications:

| | |
|---------------|------------|
| RPM | 0 – 1,400 |
| BPM | 0 – 4,900 |
| Impact Energy | 1.7 ft-lbs |



Includes: (2) M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

M18™ 7/8" SDS Plus Rotary Hammer Kit

MTL2605-22

Bare Tool: MTL2605-20

Specifications:

| | |
|---------------|------------|
| RPM | 0 – 1,400 |
| BPM | 0 – 4,800 |
| Impact Energy | 1.4 ft-lbs |



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

5/8" SDS Plus Rotary Hammer Kit

MTL5263-21

Specifications:

| | |
|---------------|------------|
| RPM | 0 – 3,700 |
| BPM | 0 – 4,700 |
| Impact Energy | 1.5 ft-lbs |



Includes: (1) Carrying Case, (1) Depth Rod, (1) Side Handle

1-1/8" SDS Plus Rotary Hammer Kit

MTL5268-21

Specifications:

| | |
|---------------|------------|
| RPM | 0 – 1,500 |
| BPM | 0 – 5,500 |
| Impact Energy | 3.6 ft-lbs |



Includes: (1) Depth Rod, (1) Side Handle, (1) Carrying Case

1-3/4" SDS Max Rotary Hammer

MTL5426-21

Specifications:

| | |
|------------------|------------|
| Fastening Torque | 210 ft-lbs |
| IPM | 0 – 3,200 |
| RPM | 0 – 2,500 |



Includes: (1) Carrying Case, (1) Side Handle

2" SDS Max Demolition Hammer

MTL5339-21

Specifications:

| | |
|---------------|-------------|
| RPM | 125 – 250 |
| BPM | 975 – 1,950 |
| Impact Energy | 19.9 ft-lbs |



Includes: (2) Auxiliary Handle, (1) Carrying Case

COMING SOON!

HIGH DEMAND™
9.0
Battery



M18 FUEL
1-9/16" SDS Max Rotary Hammer

Specifications:

| | |
|------------------|-------------------------------|
| RPM | 0 – 440 |
| BPM | 0 – 3,000 |
| Impact Energy | 5.0 ft-lbs |
| 2-Mode Operation | Rotary Hammer and Hammer Only |
| Weight | 13.75 lbs |

M18 REDLITHIUM
HIGH DEMAND™ 9.0 Battery

**DELIVERS MAXIMUM
POWER FOR THE MOST
DEMANDING APPLICATIONS**



UP TO
5X
MORE
RUN-TIME

UP TO
35%
MORE
POWER

RUNS
UP TO
60%
COOLER

M12**M18****BATTERIES & CHARGERS****REDLITHIUM™****M18™ 5.0 Ah Battery**

MTL48-11-1850

**M18™ 5.0 Ah Battery 2 Pack**

MTL48-11-1852

**M18™ 5.0 Ah Battery Starter Kit**

MTL48-11-1850

**Includes:** (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ & M12™ Multi-Voltage Charger**M12™ 4.0 Ah Battery**

MTL48-11-2440

**M18™ 4.0 Ah Battery**

MTL48-11-1840

**M12™ 2.0 Ah Battery**

MTL48-11-2420

**M18™ 3.0 Ah Battery 2 Pack**

MTL48-11-1822

**M12™/ M18™ Rapid Charging Station**

MTL48-59-1807

**M18™ 3.0 Ah Battery**

MTL48-11-1828

**M18™ 2.0 Ah Battery**

MTL48-11-1820




Milwaukee

HAND TOOLS



**ULTIMATE PRODUCTIVITY.
SUPERIOR PERFORMANCE.**



HOLLOWCORE™ Magnetic Nut Drivers



| MET Part # | Description |
|------------|--|
| 48-22-2520 | 3/16" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2521 | 1/4" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2522 | 5/16" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2523 | 11/32" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2524 | 3/8" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2525 | 7/16" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2526 | 1/2" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2527 | 9/16" HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2531 | 5mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2532 | 5.5mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2533 | 6mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2534 | 7mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2535 | 8mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2536 | 10mm HOLLOWCORE™ Magnetic Nut Driver |
| 48-22-2537 | 13mm HOLLOWCORE™ Magnetic Nut Driver |

Hollow Shaft Nut Drivers



| MET Part # | Description |
|------------|--------------------------------|
| 48-22-2420 | 3/16" Hollow Shaft Nut Driver |
| 48-22-2421 | 1/4" Hollow Shaft Nut Driver |
| 48-22-2422 | 5/16" Hollow Shaft Nut Driver |
| 48-22-2423 | 11/32" Hollow Shaft Nut Driver |
| 48-22-2424 | 3/8" Hollow Shaft Nut Driver |
| 48-22-2425 | 7/16" Hollow Shaft Nut Driver |
| 48-22-2426 | 1/2" Hollow Shaft Nut Driver |
| 48-22-2427 | 9/16" Hollow Shaft Nut Driver |
| 48-22-2431 | 5mm Hollow Shaft Nut Driver |
| 48-22-2432 | 5.5mm Hollow Shaft Nut Driver |
| 48-22-2433 | 6mm Hollow Shaft Nut Driver |
| 48-22-2434 | 7mm Hollow Shaft Nut Driver |
| 48-22-2435 | 8mm Hollow Shaft Nut Driver |
| 48-22-2436 | 10mm Hollow Shaft Nut Driver |
| 48-22-2437 | 13mm Hollow Shaft Nut Driver |

11IN1 Screwdrivers



| MET Part # | Description |
|------------|-----------------------------|
| 48-22-2113 | 11IN1 Screwdriver |
| 48-22-2114 | 11IN1 Screwdriver w/ Square |
| 48-22-2110 | 4 Pc Replacement Bit Set |

Pliers



| MET Part # | Description |
|------------|---------------------------------|
| 48-22-3069 | 6IN1 Combination Pliers |
| 48-22-3068 | 6IN1 Long Nose Pliers |
| 48-22-3309 | 6IN1 Lineman's Pliers |
| 48-22-3210 | 10" Tongue & Groove Pliers |
| 48-22-3212 | 12" Tongue & Groove Pliers |
| 48-22-3108 | 8" Quick Adjust Reaming Pliers |
| 48-22-3110 | 10" Quick Adjust Reaming Pliers |
| 48-22-3112 | 12" Quick Adjust Reaming Pliers |

Screwdrivers



| MET Part # | Description |
|------------|---|
| 48-22-2011 | #1 Phillips Screwdriver (3") |
| 48-22-2012 | #2 Phillips Screwdriver (4") |
| 48-22-2013 | #3 Phillips Screwdriver (6") |
| 48-22-2031 | 3/16" Cabinet Screwdriver (3") |
| 48-22-2032 | 3/16" Cabinet Screwdriver (6") |
| 48-22-2033 | 3/16" Cabinet Screwdriver (8") |
| 48-22-2041 | #1 ECX™ Screwdriver (4") |
| 48-22-2042 | #2 ECX™ Screwdriver (4") |
| 48-22-2051 | #1 Square Screwdriver (4") |
| 48-22-2052 | #2 Square Screwdriver (4") |
| 48-22-2053 | #3 Square Screwdriver (6") |
| 48-22-2021 | 1/4" Slotted Demolition Screwdriver (4") |
| 48-22-2022 | 5/16" Slotted Demolition Screwdriver (6") |
| 48-22-2023 | 3/8" Slotted Demolition Screwdriver (8") |

10IN1 Screwdrivers



| MET Part # | Description |
|------------|---------------------------------------|
| 48-22-2101 | 10IN1 ECX™ Multi-Bit Driver |
| 48-22-2102 | 10IN1 Square Multi-Bit Driver |
| 48-22-2301 | 10IN1 Ratchet ECX™ Multi-Bit Driver |
| 48-22-2302 | 10IN1 Ratchet Square Multi-Bit Driver |
| 48-22-2103 | 10IN1 TORX® Key Driver |
| 48-22-2104 | 10IN1 SAE Hex Key Driver |
| 48-22-2106 | 10IN1 Metric Hex Key Driver |

Insulated Screwdrivers



| MET Part # | Description |
|------------|--|
| 48-22-2211 | #1 Phillips Insulated Screwdriver (3") |
| 48-22-2212 | #2 Phillips Insulated Screwdriver (4") |
| 48-22-2213 | #3 Phillips Insulated Screwdriver (6") |
| 48-22-2221 | 1/4" Slotted Insulated Screwdriver (6") |
| 48-22-2222 | 5/16" Slotted Insulated Screwdriver (7") |
| 48-22-2223 | 3/8" Slotted Insulated Screwdriver (8") |
| 48-22-2224 | 3/8" Slotted Insulated Screwdriver (10") |
| 48-22-2231 | 3/16" Cabinet Insulated Screwdriver (4") |
| 48-22-2232 | 3/16" Cabinet Insulated Screwdriver (6") |
| 48-22-2233 | 3/16" Cabinet Insulated Screwdriver (8") |
| 48-22-2241 | #1 ECX™ Insulated Screwdriver (4") |
| 48-22-2242 | #2 ECX™ Insulated Screwdriver (4") |
| 48-22-2251 | #1 Square Insulated Screwdriver (3") |
| 48-22-2252 | #2 Square Insulated Screwdriver (4") |
| 48-22-2253 | #3 Square Insulated Screwdriver (6") |

Milwaukee

ACCESSORIES



DISRUPTIVE INNOVATION



BI-METAL HOLE SAWS

| Size | Metric | Hanging Container | Shrink Wrap |
|----------|--------|-------------------|-------------|
| 5/8" | 16 mm | 49-56-0012 | 49-56-9603 |
| 11/16" | 18 mm | 49-56-0017 | 49-56-9604 |
| 3/4" | 19 mm | 49-56-0023 | 49-56-9605 |
| 13/16" | 21 mm | 49-56-0027 | 49-56-9606 |
| 7/8" | 22 mm | 49-56-0032 | 49-56-9607 |
| 15/16" | 24 mm | 49-56-0037 | 49-56-9608 |
| 1" | 25 mm | 49-56-0043 | 49-56-9609 |
| 1-1/16" | 27 mm | 49-56-0047 | 49-56-9610 |
| 1-1/8" | 29 mm | 49-56-0052 | 49-56-9611 |
| 1-3/16" | 30 mm | 49-56-0057 | 49-56-9612 |
| 1-1/4" | 32 mm | 49-56-0062 | 49-56-9613 |
| 1-5/16" | 33 mm | 49-56-0067 | 49-56-9614 |
| 1-3/8" | 35 mm | 49-56-0072 | 49-56-9615 |
| 1-7/16" | 37 mm | 49-56-0077 | 49-56-9616 |
| 1-1/2" | 38 mm | 49-56-0082 | 49-56-9617 |
| 1-9/16" | 40 mm | 49-56-0087 | 49-56-9618 |
| 1-5/8" | 41 mm | 49-56-0092 | 49-56-9619 |
| 1-11/16" | 43 mm | 49-56-0097 | 49-56-9620 |
| 1-3/4" | 44 mm | 49-56-0102 | 49-56-9621 |
| 1-13/16" | 46 mm | 49-56-0107 | 49-56-9622 |
| 1-7/8" | 48 mm | 49-56-0112 | 49-56-9623 |
| 2" | 51 mm | 49-56-0117 | 49-56-9624 |
| 2-1/16" | 52 mm | 49-56-0122 | 49-56-9625 |
| 2-1/8" | 54 mm | 49-56-0127 | 49-56-9626 |
| 2-1/4" | 57 mm | 49-56-0132 | 49-56-9628 |

| Size | Metric | Hanging Container | Shrink Wrap |
|---------|--------|-------------------|-------------|
| 2-5/16" | 59 mm | 49-56-0137 | 49-56-9629 |
| 2-3/8" | 60 mm | 49-56-0142 | 49-56-9630 |
| 2-1/2" | 64 mm | 49-56-0147 | 49-56-9631 |
| 2-9/16" | 65 mm | 49-56-0153 | 49-56-9632 |
| 2-5/8" | 67 mm | 49-56-0158 | 49-56-9633 |
| 2-3/4" | 70 mm | 49-56-0163 | 49-56-9635 |
| 2-7/8" | 73 mm | 49-56-0167 | 49-56-9636 |
| 3" | 76 mm | 49-56-0173 | 49-56-9637 |
| 3-1/8" | 79 mm | 49-56-0177 | 49-56-9638 |
| 3-1/4" | 83 mm | 49-56-0183 | 49-56-9639 |
| 3-3/8" | 86 mm | 49-56-0187 | 49-56-9640 |
| 3-1/2" | 89 mm | 49-56-0193 | 49-56-9641 |
| 3-5/8" | 92 mm | 49-56-0197 | 49-56-9642 |
| 3-3/4" | 95 mm | 49-56-0203 | 49-56-9643 |
| 3-7/8" | 98 mm | 49-56-0207 | 49-56-9644 |
| 4" | 102 mm | 49-56-0213 | 49-56-9645 |
| 4-1/8" | 105 mm | 49-56-0217 | 49-56-9646 |
| 4-1/4" | 108 mm | 49-56-0223 | 49-56-9647 |
| 4-3/8" | 111 mm | 49-56-0227 | 49-56-9648 |
| 4-1/2" | 114 mm | 49-56-0233 | 49-56-9649 |
| 4-3/4" | 121 mm | 49-56-0237 | 49-56-9650 |
| 5" | 127 mm | 49-56-0243 | 49-56-9652 |
| 5-1/2" | 140 mm | 49-56-0247 | 49-56-9654 |
| 6" | 152 mm | 49-56-0253 | 49-56-9656 |



METAL CUTTING SAWZALL® BLADES

DOUBLE DUTY
UPGRADE

LONGEST
LIFE OF ANY SAWZALL®
BLADE EVER

STRONGEST
SHEAR'S TANG
FOR INCREASED
DURABILITY

STIFFEST
SHEAR'S TANG
FOR RIGIDITY

CHISEL POINT

*BASE ON ANY SAWZALL® TOOTH DESIGN



The Torch™ metal-cutting blades are designed to provide tough, straight cuts in all metal materials. Choose The Torch™ blades when you need straight cuts in pipe or tube, or when you need greater tooth durability in hollow materials like strut or conduit. The Torch™ blades are 1" tall and .042" thick.

Thin Kerf metal-cutting blades are designed to provide fast, flexible cuts in all metal materials. Choose Thin Kerf blades when you need flexibility for flush cuts or scroll cuts, or when you want faster cuts in solid materials like threaded rod or bar stock. Thin Kerf metal-cutting blades are 3/4" tall and .035" thick.

THE TORCH™ TOUGH STRAIGHT CUTS

| TPI | Length | Materials | THE TORCH™ TOUGH STRAIGHT CUTS | | | | |
|-----|--------|-----------|--------------------------------|------------|----------|------------|------------|
| | | | 5 Packs | 25 Packs | 50 Packs | Bulk (25) | Bulk (100) |
| 10 | 4" | | - | - | - | - | - |
| 10 | 6" | | 48-00-5712 | 48-00-8712 | - | 48-01-2712 | 48-01-7712 |
| 10 | 9" | | 48-00-5713 | 48-00-8713 | - | 48-01-2713 | 48-01-7713 |
| 10 | 12" | | 48-00-5714 | - | - | 48-01-2714 | - |
| 14 | 4" | | - | - | - | - | - |
| 14 | 6" | | 48-00-5782 | 48-00-8782 | - | 48-01-2782 | 48-01-7782 |
| 14 | 9" | | 48-00-5787 | 48-00-8787 | - | 48-01-2787 | 48-01-7787 |
| 14 | 12" | | 48-00-5794 | - | - | 48-01-2794 | - |
| 18 | 4" | | - | - | - | - | - |
| 18 | 6" | | 48-00-5784 | 48-00-8784 | - | 48-01-2784 | 48-01-7784 |
| 18 | 9" | | 48-00-5788 | 48-00-8788 | - | 48-01-2788 | 48-01-7788 |
| 18 | 12" | | 48-00-5789 | 48-00-8789 | - | 48-01-2789 | 48-01-7789 |
| 24 | 4" | | - | - | - | - | - |
| 24 | 6" | | 48-00-5786 | - | - | - | - |
| 24 | 9" | | 48-00-5790 | - | - | - | - |
| 24 | 12" | | 48-00-5791 | - | - | - | - |

THIN KERF FAST FLEXIBLE CUTS

| THIN KERF FAST FLEXIBLE CUTS | | | | |
|------------------------------|------------|------------|------------|------------|
| 5 Packs | 25 Packs | 50 Packs | Bulk (25) | Bulk (100) |
| 48-00-5090 | - | - | - | - |
| 48-00-5092 | - | 48-01-6092 | - | 48-01-7092 |
| - | - | - | - | - |
| - | - | - | - | - |
| 48-00-5181 | - | - | - | - |
| 48-00-5182 | 48-00-8182 | 48-01-6182 | 48-01-2182 | 48-01-7182 |
| 48-00-5187 | - | 48-01-6187 | 48-01-2187 | 48-01-7187 |
| - | - | - | - | - |
| 48-00-5183 | - | - | - | - |
| 48-00-5184 | 48-00-8184 | 48-01-6184 | 48-01-2184 | 48-01-7184 |
| 48-00-5188 | - | 48-01-6188 | 48-01-2188 | 48-01-7188 |
| 48-00-5189 | - | 48-01-6189 | - | 48-01-7189 |
| 48-00-5185 | - | - | - | - |
| 48-00-5186 | 48-00-8186 | 48-01-6186 | 48-01-2186 | 48-01-7186 |
| - | - | - | - | - |
| - | - | - | - | - |

WOOD CUTTING SAWZALL® BLADES



The Ax™ wood-cutting blades are designed to provide tough, straight cuts in nail-embedded wood and engineered lumber. Choose The Ax™ blades for straighter door and window cut-outs or for greater tooth durability when cutting a lot of nails. The Ax™ blades are 1" tall and .060" thick.

Thin Kerf wood-cutting blades are designed to provide fast, flexible cuts in nail-embedded wood and engineered lumber. Choose Thin Kerf blades for flush cuts and scroll cuts or for slightly faster cutting in dimensional lumber, plywood and OSB. Thin Kerf wood-cutting blades are 3/4" tall and .050" thick.

| TPI | Length | Materials | THE AX™ TOUGH STRAIGHT CUTS | | | | THIN KERF FAST FLEXIBLE CUTS | | | | |
|-----|--------|-----------|-----------------------------|------------|------------|------------|------------------------------|------------|------------|------------|------------|
| | | | 5 Packs | 25 Packs | Bulk (25) | Bulk (100) | 5 Packs | 25 Packs | 50 Packs | Bulk (25) | Bulk (100) |
| 5 | 6" | | 48-00-5021 | 48-00-8021 | 48-01-2021 | 48-01-7021 | 48-00-5035 | — | 48-01-6035 | 48-01-2035 | 48-01-7035 |
| 5 | 9" | | 48-00-5026 | 48-00-8026 | 48-01-2026 | 48-01-7026 | 48-00-5036 | 48-00-8036 | 48-01-6036 | 48-01-2036 | 48-01-7036 |
| 5 | 12" | | 48-00-5027 | 48-00-8027 | 48-01-2027 | 48-01-7027 | 48-00-5037 | — | 48-01-6037 | 48-01-2037 | 48-01-7037 |

GENERAL PURPOSE SAWZALL® BLADES

Both Thin Kerf and The Wrecker™ general purpose blades are designed to handle the broadest spectrum of applications. Choose general purpose blades when cutting wood, plastic and metal at the same time or when you need to quickly switch between applications without changing your blade.

WRECKER™
TACKLE ANYTHING



The Wrecker™ general purpose blades are designed for true demolition work. Choose The Wrecker™ blades when you need tough cuts in nail-embedded wood, plaster and ferrous and non-ferrous metals. The Wrecker™ blades are 1" tall and .060" thick.

Thin Kerf general purpose blades are designed to provide fast, flexible cuts in woods, plastics and metals. Thin Kerf general purpose blades are 3/4" tall and .050" thick.

| TPI | Length | Materials | THE WRECKER™ TOUGH STRAIGHT CUTS | | | | THIN KERF FAST FLEXIBLE CUTS | | | | |
|------|--------|-----------|----------------------------------|------------|------------|------------|------------------------------|------------|------------|------------|------------|
| | | | 5 Packs | 25 Packs | Bulk (25) | Bulk (100) | 5 Packs | 25 Packs | 50 Packs | Bulk (25) | Bulk (100) |
| 8 | 6" | | 48-00-5701 | 48-00-8701 | 48-01-2701 | 48-01-7701 | — | — | — | — | — |
| 8 | 9" | | 48-00-5706 | 48-00-8706 | 48-01-2706 | 48-01-7706 | — | — | — | — | — |
| 8 | 12" | | 48-00-5711 | 48-00-8711 | 48-01-2711 | 48-01-7711 | — | — | — | — | — |
| 8/12 | 6" | | — | — | — | — | 48-00-5091 | — | 48-01-6091 | — | 48-01-7091 |
| 8/12 | 8" | | — | — | — | — | 48-00-5093 | 48-00-8093 | 48-01-6093 | 48-01-2093 | 48-01-7093 |
| 8/12 | 12" | | — | — | — | — | 48-00-5094 | — | 48-01-6094 | 48-01-2094 | — |

DRY CUT METAL CIRCULAR SAW BLADES

LONG LIFE

- Micro ground carbide teeth stay sharper longer

ACCURATE CUTS

- Fully hardened, tensioned steel plate prevents warping

FAST CUTTING

- Extra thin kerf for faster, cleaner cuts



| | Diameter | Part Number | # of Teeth | Tooth Material | Arbor | Max RPM | Pkg Qty | Materials |
|----------|----------|-------------|------------|----------------|-------|---------|---------|-------------|
| CORDLESS | 5-3/8" | 48-40-4070 | 30 | Carbide | 20mm | 4,200 | 1 | Ferrous |
| | 5-3/8" | 48-40-4075 | 50 | Carbide | 20mm | 4,200 | 1 | Non-Ferrous |
| | 6-1/2" | 48-40-4005 | 60 | Carbide | 5/8" | 4,200 | 1 | Non-Ferrous |
| | 6-1/2" | 48-40-4015 | 48 | Carbide | 5/8" | 4,200 | 1 | Ferrous |
| | 6-7/8" | 48-40-4006 | 52 | Carbide | 20mm | 4,200 | 1 | Non-Ferrous |
| | 6-7/8" | 48-40-4016 | 36 | Carbide | 20mm | 4,200 | 1 | Ferrous |
| CORDED | 8" | 48-40-4515 | 42 | Cermet | 5/8" | 5,000 | 1 | Ferrous |
| | 8" | 48-40-4520 | 50 | Cermet | 5/8" | 5,000 | 1 | Ferrous |
| | 8" | 48-40-4530 | 60 | Carbide | 5/8" | 5,000 | 1 | Non-Ferrous |
| | 8" | 48-40-4540 | 60 | Carbide | 5/8" | 5,000 | 1 | Non-Ferrous |

BI-METAL PORTABLE BAND SAW BLADES

MAXIMUM DURABILITY

- Matrix II high speed steel protects teeth from chipping and breaking

EXTENDED LIFE

- Alloy backing steel resists kinking and snapping

CLEAN CUTS

- Precision formed teeth cut quickly and smoothly

Deep Cut Blades

- Designed to maximize performance of any portable band saw that takes a 44-7/8" blade

| Length | TPI | 1 Pack | 2 Pack | 3 Pack | Bulk | Qty |
|---------|-------|------------|------------|------------|------------|-----|
| 44-7/8" | 10 | 48-39-0500 | — | 48-39-0501 | 48-39-0502 | 100 |
| 44-7/8" | 14 | 48-39-0510 | 48-39-0514 | 48-39-0511 | 48-39-0512 | 100 |
| 44-7/8" | 18 | 48-39-0520 | 48-39-0524 | 48-39-0521 | 48-39-0522 | 100 |
| 44-7/8" | 24 | 48-39-0530 | 48-39-0534 | 48-39-0531 | 48-39-0532 | 100 |
| 44-7/8" | 10/14 | 48-39-0550 | 48-39-0554 | 48-39-0551 | 48-39-0552 | 100 |
| 44-7/8" | 14/18 | 48-39-0560 | — | 48-39-0561 | 48-39-0562 | 100 |

Compact Blades

- Designed to maximize performance of Milwaukee® Compact Band Saws

| Length | TPI | 1 Pack | 3 Pack | Bulk | Qty |
|---------|-----|------------|------------|------------|-----|
| 35-3/8" | 10 | 48-39-0508 | 48-39-0509 | 48-39-0507 | 100 |
| 35-3/8" | 14 | 48-39-0518 | 48-39-0519 | 48-39-0517 | 100 |
| 35-3/8" | 18 | 48-39-0528 | 48-39-0529 | 48-39-0527 | 100 |
| 35-3/8" | 24 | 48-39-0538 | 48-39-0539 | 48-39-0537 | 100 |

SDS+ ROTARY HAMMER BITS

2-CUTTER SDS+ CARBIDE BITS

ACCURATE STARTS

- Centering point ensures correct hole placement

FAST DRILLING

- Chisel shaped head for fast drilling in hard materials
- High volume flute entrance quickly channels debris to the flute



4 FLUTED SPIRAL IN SMALL DIAMETERS

- Fast debris removal
- Minimizes bending and breaking
- Minimizes vibrations

| Size | Useable Length | Overall Length | Individual Part Number | Bulk Part Number | Bulk Qty | Monster Pack Part Number | Qty |
|-------|----------------|----------------|------------------------|------------------|----------|--------------------------|-----|
| 5/32" | 2" | 4-1/2" | 48-20-7400 | 48-20-7500 | 25 | - | - |
| 5/32" | 4" | 6" | 48-20-7401 | 48-20-7501 | 25 | - | - |
| 3/16" | 2" | 4-1/2" | 48-20-7410 | 48-20-7510 | 25 | 48-20-7810 | 200 |
| 3/16" | 4" | 6" | 48-20-7411 | 48-20-7511 | 25 | 48-20-7811 | 200 |
| 3/16" | 6" | 8" | 48-20-7412 | 48-20-7512 | 25 | - | - |
| 3/16" | 8" | 10" | 48-20-7413 | 48-20-7513 | 25 | - | - |
| 3/16" | 10" | 12" | 48-20-7414 | 48-20-7514 | 25 | - | - |
| 3/16" | 12" | 14" | 48-20-7415 | 48-20-7515 | 25 | - | - |
| 3/16" | 14" | 16" | 48-20-7416 | 48-20-7516 | 25 | - | - |
| 7/32" | 4" | 6" | 48-20-7421 | 48-20-7521 | 25 | - | - |
| 7/32" | 6" | 8" | 48-20-7422 | 48-20-7522 | 25 | - | - |
| 7/32" | 9" | 11" | 48-20-7424 | 48-20-7524 | 25 | - | - |
| 7/32" | 12" | 14" | 48-20-7425 | 48-20-7525 | 25 | - | - |
| 7/32" | 14" | 16" | 48-20-7426 | 48-20-7526 | 25 | - | - |
| 1/4" | 2" | 4-1/2" | 48-20-7430 | 48-20-7530 | 25 | 48-20-7830 | 200 |
| 1/4" | 4" | 6" | 48-20-7431 | 48-20-7531 | 25 | 48-20-7831 | 200 |
| 1/4" | 6" | 8" | 48-20-7432 | 48-20-7532 | 25 | - | - |
| 1/4" | 9" | 11" | 48-20-7434 | 48-20-7534 | 25 | - | - |
| 1/4" | 12" | 14" | 48-20-7435 | 48-20-7535 | 25 | - | - |
| 1/4" | 14" | 16" | 48-20-7436 | 48-20-7536 | 25 | - | - |
| 1/4" | 18" | 20" | 48-20-7438 | - | - | - | - |
| 5/16" | 4" | 6" | 48-20-7441 | 48-20-7541 | 25 | 48-20-7841 | 150 |
| 5/16" | 10" | 12" | 48-20-7444 | - | - | - | - |
| 3/8" | 4" | 6" | 48-20-7451 | 48-20-7551 | 20 | 48-20-7851 | 125 |
| 3/8" | 6" | 8" | 48-20-7452 | - | - | - | - |
| 3/8" | 8" | 10" | 48-20-7453 | - | - | - | - |
| 3/8" | 10" | 12" | 48-20-7454 | 48-20-7554 | 20 | - | - |
| 3/8" | 16" | 18" | 48-20-7457 | - | - | - | - |
| 3/8" | 22" | 24" | 48-20-7459 | - | - | - | - |

| Size | Useable Length | Overall Length | Individual Part Number | Bulk Part Number | Bulk Qty | Monster Pack Part Number | Qty |
|--------|----------------|----------------|------------------------|------------------|----------|--------------------------|-----|
| 7/16" | 4" | 6" | 48-20-7461 | - | - | - | - |
| 7/16" | 10" | 12-1/2" | 48-20-7464 | - | - | - | - |
| 7/16" | 16" | 18" | 48-20-7467 | - | - | - | - |
| 1/2" | 4" | 6" | 48-20-7471 | 48-20-7571 | 15 | 48-20-7871 | 100 |
| 1/2" | 8" | 10" | 48-20-7473 | - | - | - | - |
| 1/2" | 10" | 12" | 48-20-7474 | 48-20-7574 | 15 | - | - |
| 1/2" | 16" | 18" | 48-20-7477 | - | - | - | - |
| 1/2" | 22" | 24" | 48-20-7479 | - | - | - | - |
| 9/16" | 4" | 6-1/2" | 48-20-7481 | - | - | - | - |
| 9/16" | 10" | 12-1/2" | 48-20-7484 | - | - | - | - |
| 9/16" | 16" | 18" | 48-20-7487 | - | - | - | - |
| 5/8" | 4" | 6" | 48-20-7601 | - | - | - | - |
| 5/8" | 6" | 8" | 48-20-7602 | 48-20-7702 | 10 | - | - |
| 5/8" | 10" | 12" | 48-20-7604 | - | - | - | - |
| 5/8" | 16" | 18" | 48-20-7607 | - | - | - | - |
| 5/8" | 22" | 24" | 48-20-7609 | - | - | - | - |
| 11/16" | 6" | 8" | 48-20-7058 | - | - | - | - |
| 3/4" | 6" | 8" | 48-20-7061 | - | - | - | - |
| 3/4" | 8" | 10" | 48-20-7063 | - | - | - | - |
| 3/4" | 10" | 12" | 48-20-7065 | - | - | - | - |
| 3/4" | 16" | 18" | 48-20-7066 | - | - | - | - |
| 3/4" | 22" | 24" | 48-20-7067 | - | - | - | - |
| 27/32" | 6" | 8" | 48-20-7069 | - | - | - | - |
| 7/8" | 6" | 8" | 48-20-7071 | - | - | - | - |
| 7/8" | 10" | 12" | 48-20-7072 | - | - | - | - |
| 7/8" | 16" | 18" | 48-20-7075 | - | - | - | - |
| 1" | 8" | 10" | 48-20-7080 | - | - | - | - |
| 1" | 16" | 18" | 48-20-7085 | - | - | - | - |

SDS-MAX ROTARY HAMMER BITS

LONG LIFE

- Brazing formula optimizes drilling for up to 20% longer life

FAST DUST REMOVAL

- Unique flute geometry provides efficient dust removal

PRECISE ROUND HOLES

- Centering point and 4-Cutter design provide accurate and precise round holes

4-CUTTER WITH 4X90° SYMMETRY

- Will not lock-up in rebar

| Size | Useable Length | Overall Length | 2-Cutter Part Number | 4-Cutter Part Number |
|--------|----------------|----------------|----------------------|----------------------|
| 3/8" | 7-1/2" | 13" | 48-20-3901 | |
| 1/2" | 7-1/2" | 13" | 48-20-3902 | |
| 1/2" | 11-1/2" | 17" | 48-20-3903 | |
| 1/2" | 15-1/2" | 21" | 48-20-3904 | |
| 1/2" | 22-1/2" | 28" | 48-20-3905 | |
| 1/2" | 30-1/2" | 36" | 48-20-3906 | |
| 1/2" | 54" | 60" | 48-20-3909 | |
| 9/16" | 7-1/2" | 13" | 48-20-3910 | |
| 9/16" | 15-1/2" | 21" | 48-20-3912 | |
| 5/8" | 7-1/2" | 13" | | 48-20-3916 |
| 5/8" | 11-1/2" | 17" | | 48-20-3917 |
| 5/8" | 15-1/2" | 21" | | 48-20-3918 |
| 5/8" | 30-1/2" | 36" | | 48-20-3922 |
| 5/8" | 54" | 60" | | 48-20-3923 |
| 11/16" | 15-1/2" | 21" | | 48-20-3926 |
| 3/4" | 8" | 13" | | 48-20-3930 |
| 3/4" | 12" | 17" | | 48-20-3931 |
| 3/4" | 16" | 21" | | 48-20-3932 |
| 3/4" | 31" | 36" | | 48-20-3936 |



| Size | Useable Length | Overall Length | 2-Cutter Part Number | 4-Cutter Part Number |
|---------|----------------|----------------|----------------------|----------------------|
| 13/16" | 16" | 21" | | 48-20-3938 |
| 7/8" | 8" | 13" | | 48-20-3944 |
| 7/8" | 12" | 17" | | 48-20-3945 |
| 7/8" | 16" | 21" | | 48-20-3946 |
| 7/8" | 31" | 36" | | 48-20-3949 |
| 1" | 8" | 13" | | 48-20-3952 |
| 1" | 12" | 17" | | 48-20-3953 |
| 1" | 16" | 21" | | 48-20-3954 |
| 1" | 31" | 36" | | 48-20-3956 |
| 1-1/16" | 18" | 23" | | 48-20-3958 |
| 1-1/8" | 12" | 17" | | 48-20-3964 |
| 1-1/8" | 16" | 21" | | 48-20-3966 |
| 1-3/16" | 18" | 23" | | 48-20-3968 |
| 1-1/4" | 10" | 15" | | 48-20-3970 |
| 1-1/4" | 18" | 23" | | 48-20-3972 |
| 1-1/4" | 31" | 36" | | 48-20-3974 |
| 1-3/8" | 12" | 17" | | 48-20-3975 |
| 1-3/8" | 18" | 23" | | 48-20-3980 |
| 1-3/8" | 31" | 36" | | 48-20-3983 |
| 1-7/16" | 18" | 23" | | 48-20-3984 |
| 1-1/2" | 12" | 17" | | 48-20-3986 |
| 1-1/2" | 18" | 23" | | 48-20-3988 |
| 1-9/16" | 18" | 23" | | 48-20-3990 |
| 1-5/8" | 18" | 23" | | 48-20-3991 |
| 1-3/4" | 18" | 23" | | 48-20-3992 |
| 2" | 18" | 23" | | 48-20-3993 |

ANNULAR CUTTERS



FASTER CUTTING

- Thinner wall design for faster, more efficient cutting

LONG LIFE

- Proprietary steel, optimized for steel cutting

UNIVERSAL SHANK

- Fits directly into Milwaukee® compact magnetic drill press
- Works with 3/4" Weldon® style shank arbor

| Size | 1" Depth | 2" Depth |
|---------|------------|------------|
| 1/2" | 49-59-0500 | 49-59-2050 |
| 9/16" | 49-59-0562 | 49-59-2056 |
| 5/8" | 49-59-0625 | 49-59-2063 |
| 11/16" | 49-59-0687 | 49-59-2069 |
| 3/4" | 49-59-0750 | 49-59-2075 |
| 13/16" | 49-59-0812 | 49-59-2081 |
| 7/8" | 49-59-0875 | 49-59-2089 |
| 15/16" | 49-59-0937 | 49-59-2094 |
| 1" | 49-59-1000 | 49-59-2100 |
| 1-1/16" | 49-59-1062 | 49-59-2106 |
| 1-1/8" | 49-59-1125 | 49-59-2113 |
| 1-3/16" | 49-59-1187 | 49-59-2119 |
| 1-1/4" | 49-59-1250 | 49-59-2125 |

| Size | 1" Depth | 2" Depth |
|----------|------------|------------|
| 1-5/16" | 49-59-1312 | 49-59-2131 |
| 1-3/8" | 49-59-1375 | 49-59-2138 |
| 1-7/16" | 49-59-1437 | 49-59-2144 |
| 1-1/2" | 49-59-1500 | 49-59-2150 |
| 1-9/16" | 49-59-1562 | 49-59-2156 |
| 1-5/8" | 49-59-1625 | 49-59-2163 |
| 1-11/16" | 49-59-1687 | 49-59-2169 |
| 1-3/4" | 49-59-1750 | 49-59-2175 |
| 1-13/16" | 49-59-1812 | 49-59-2181 |
| 1-7/8" | 49-59-1875 | 49-59-2188 |
| 1-15/16" | 49-59-1937 | 49-59-2194 |
| 2" | 49-59-2000 | 49-59-2200 |



Nothing but **HEAVY DUTY**®

LIGHTNING MAX REPAIR

Milwaukee® understands the unpredictability of the jobsite and the need for fast, reliable repairs and replacements. Through our Lightning Max Repair Program we are committed to providing you the best service so you can minimize downtime and get the job done.

SPEED: Repair of your tool in one week or less

PAY LESS, NOT MORE: Guaranteed to never pay more than the quoted Lightning Max Repair price

RELIABILITY: All repairs are serviced by experienced, certified factory technicians

QUALITY: Only genuine Milwaukee® parts used

WHERE TO GO FOR LIGHTNING MAX REPAIRS

eSERVICE

Solution for quick, convenient repairs, best for smaller tool quantities.

- **Fedex shipping to Milwaukee® repair facility**
- **Your tool returned directly to you - No need to pick it up**
- **Go to www.milwaukeetool.ca/eService**



FACTORY SERVICE

BEST IN CLASS SERVICE BY OUR FACTORY TRAINED SERVICE TEAM

Factory Service Centers also carry the widest variety of Milwaukee® Tools and Accessories for all your needs.

1-800-268-4015

Vaughan

140 Fernstaff Court, Unit 4
Vaughan ON L4K 3L8

Edmonton

14506 – 115th Avenue NW
Edmonton AB T5M 3B9

Vancouver

9000 Bill Fox Way, Unit 103A
Burnaby BC V5J 5J3

Saskatoon

Unit 630 3530 Millar Ave
Saskatoon SK S7P 0B3

Halifax

Unit 102 50 Akerley Blvd
Dartmouth NS B3B 1R8

POWER TOOLS

Drills 5-6

Impact Wrenches and Drivers.....6-7

Cutting.....7-8

Circular Saws..... 8

Bandsaws 8

Metal Working.....9

SDS Rotary Hammers 10

Batteries & Chargers 11



HAND TOOLS

Hand Tools..... 13



ACCESSORIES

Bi-Metal Hole Saws..... 15

Metal Cutting SAWZALL® Blades 15

Wood Cutting SAWZALL® Blades 16

General Purpose SAWZALL® Blades..... 16

Dry Cut Metal Circular Saw Blades..... 16

Bi-Metal Portable Band Saw Blades..... 17

SDS+ Rotary Hammer Bits..... 17

SDS-MAX Rotary Hammer Bits..... 18

Annular Cutters..... 18





COMING SOON!

NEW!

Specialty Hand Tools



Ask your Milwaukee® rep for details.

MILWAUKEE TOOL CANADA
7303 Warden Avenue
Suite 202
Markham, ON
L3R 5Y6
www.milwaukeetool.ca

**ACKLANDS
GRAINGER®**
INDUSTRIAL • SAFETY • FASTENERS