Electrical Sector Solutions

Volume 4: Circuit Protection

EATON

Powering Business Worldwide

Volume 1—Residential and Light Commercial 1

Volume 2—Commercial Distribution 2

Volume 3—Power Distribution and Control Assemblies 3

Volume 4—Circuit Protection 4

Tab 1—Miniature Circuit Breakers and Supplementary Protectors V4-T1-1

Tab 2—Molded Case Circuit Breakers V4-T2-1

Tab 3—Power Breakers, Contactors and Fuses V4-T3-1

Appendix 1—Eaton Terms & Conditions V4-A1-1

Appendix 2—Catalog Parent Number Index V4-A2-1

Appendix 3—Alphabetical Product Index V4-A3-1

Volume 5—Motor Control and Protection 5

Volume 6—Solid-State Motor Control 6

Volume 7—Logic Control, Operator Interface and Connectivity Solutions 7

Copyright

Dimensions, Weights and Ratings

Dimensions, weights and ratings given in this catalog **are approximate and should not be used for construction purposes**. Drawings containing exact dimensions are available upon request. All listed product specifications and ratings are subject to change without notice. Photographs are representative of production units.

Terms and Conditions

All prices and discounts are subject to change without notice. When price changes occur, they are published in Eaton's *Price and Availability Digest* (PAD). All orders accepted by Eaton's Electrical Sector are subject to the general terms and conditions as set forth in Appendix 1—Eaton Terms & Conditions.

Technical and Descriptive Publications

This catalog contains brief technical data for proper selection of products. Further information is available in the form of technical information publications and illustrated brochures. If additional product information is required, contact your local Eaton Products Distributor, call **1-800-525-2000** or visit our website at **www.eaton.com**.

Compliance with Nuclear Regulation 10 CFR 21

Eaton products are sold as commercial grade products not intended for application in facilities or activities licensed by the United States Nuclear Regulatory Commission for atomic purposes, under 10 CFR 21. Further certification will be required for use of these products in a safety-related application in any nuclear facility licensed by the U.S. Nuclear Regulatory Commission.

WARNING

The installation and use of Eaton products should be in accordance with the provisions of the U.S. National Electrical Code® and/or other local codes or industry standards that are pertinent to the particular end use. Installation or use not in accordance with these codes and standards could be hazardous to personnel and/or equipment.

These catalog pages do not purport to cover all details or variations in equipment, nor to provide for every possible contingency to be met in connection with installation, operation or maintenance. Should further information be desired or should particular problems arise which are not covered sufficiently for the purchaser's purposes, the matter should be referred to the local Eaton Products Distributor or Sales Office. The contents of this catalog shall not become part of or modify any prior or existing agreement, commitment or relationship. The sales contract contains the entire obligation of Eaton's Electrical Sector. The warranty contained in the contract between the parties is the sole warranty of Eaton. Any statements contained herein do not create new warranties or modify the existing warranty.

Copyright ©2017 Eaton, All Rights Reserved.

Powering Business Worldwide

Eaton is a global leader in power distribution, power quality, control and automation, and monitoring products.

At Eaton, we believe a reliable, efficient and safe power system is the foundation of every successful enterprise. Through innovative technologies, cutting-edge products and our highly skilled services team, we empower businesses around the world to achieve a powerful advantage.

In addition, Eaton is committed to creating and maintaining powerful customer relationships built on a foundation of excellence. From the products we manufacture to our dedicated customer service and support, we know what's important to you.

Solutions

Eaton takes the complexity out of power systems management with a holistic and strategic approach, leveraging our industry-leading technology, solutions and services. We focus on the following three areas in all we do:

- Reliability—maintain the appropriate level of power continuity without disruption or unexpected downtime
- Efficiency—minimize energy usage, operating costs, equipment footprint and environmental impact
- Safety—identify and mitigate electrical hazards to protect what you value most

Using the Eaton Catalog Library

As we grow, it becomes increasingly difficult to include all products in one or two comprehensive catalogs. Knowing that each user has their specific needs, we have created a library of catalogs for our products that when complete, will contain 15 volumes. Since the volumes will continuously be a work in progress and updated, each volume will stand alone. Refer to our volume directory, MZ08100001E, for a quick glance of where to look for the products you need. The 15 volumes include:

- Volume 1—Residential and Light Commercial (CA08100002E)
- Volume 2—Commercial Distribution (CA08100003E)
- Volume 3—Power Distribution and Control Assemblies (CA08100004E)
- Volume 4—Circuit Protection (CA08100005E)
- Volume 5—Motor Control and Protection (CA08100006E)
- Volume 6—Solid-State Motor Control (CA08100007E)
- Volume 7—Logic Control, Operator Interface and Connectivity Solutions (CA08100008E)
- Volume 8—Sensing Solutions (CA08100010E)
- Volume 9—Original Equipment Manufacturer (CA08100011E)
- Volume 10—Enclosed Control (CA08100012E)
- Volume 11—Vehicle and Commercial Controls (CA08100013E)
- Volume 12—Aftermarket, Renewal Parts and Life Extension Solutions (CA08100014E)
- Volume 13—Counters, Timers and Tachometers (CA08100015E)—Available in electronic format only
- Volume 14—Fuses (CA08100016E)—Available in electronic format only
- Volume 15—Solar Inverters and Electrical Balance of System (CA08100018E)

These volumes are not all-inclusive of every product, but they are meant to be an overview of our product lines. For our full range of product solutions and additional product information, consult Eaton.com/electrical and other catalogs and product guides in our literature library. These references include:

- The Consulting Application Guide (CA08104001E)
- The Eaton Power Quality Product Guide (COR01FYA)

If you don't have the volume that contains the product or information that you are looking for, not to worry. You can access every volume of the catalog library at Eaton.com/electrical in the Literature Library.

By installing our Automatic Tab Updater (ATU), you can be sure you always have the most recent version of each volume and tab.

Icons

Green Leaf

Eaton Green Solutions are products, systems or solutions that represent Eaton benchmarks for environmental performance. The green leaf symbol is our promise that the solution has been reviewed and documented as offering exceptional, industry-leading environmental benefits to customers, consumers and our communities. Though all of Eaton's products and solutions are designed to meet or exceed applicable government standards related to protecting the environment, our products with the Green Leaf designation further provide "exceptional environmental benefit."

Learn Online

When you see the Learn Online icon, go to Eaton.com/electrical and search for the product or training page. There you will find 100-level training courses, podcasts, webcasts or games and puzzles to learn more.

Drawings Online

When you see the Drawings Online icon, go to Eaton.com/electrical and find the products page. There you will find a tab that includes helpful product drawings and illustrations.

Contact Us

If you need additional help, you can find contact information under the Customer Care heading of Eaton.com/electrical.

Miniature Circuit Breakers and Supplementary Protectors

Miniature Circuit Breakers and Supplementary Protectors

1.1 Industrial Circuit Breakers

QUICKLAG® V4-T1-2
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW V4-T1-5
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPHGFT, QPHGFT, QPGFEP, QPHGFEP V4-T1-8
Bolt-On Types BAB, QBHW, HBAX, HBAW V4-T1-11
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF V4-T1-14
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP V4-T1-17
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW V4-T1-20
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH V4-T1-24
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP V4-T1-28
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP V4-T1-31
Solenoid Operator—Remote-Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers V4-T1-34
International Rated Types HQP, BA, QC, GFMB, GFXBC V4-T1-37
Special Application Breakers, Types HQP, BA, QC V4-T1-40

1.2 UL 489 DIN Rail Miniature Circuit Breakers

FAZ-NA and FAZ-NA-L Circuit Breakers V4-T1-49

1.3 UL 1077 DIN Rail Supplementary Protectors

FAZ Circuit Breakers V4-T1-70

1.4 UL 1053 DIN Rail RCCB

UL 1053 DIN Rail RCCB 480/277 Vac V4-T1-90
UL 1053 DIN Rail RCCB 208Y/120 Vac V4-T1-96

Learn Online

Miniature Circuit Breakers and Supplementary Protectors

Contents

Description
Quick Reference

QUICKLAG

Quick Reference

Eaton's QUICKLAG Industrial Circuit Breakers ① Plug-In, Bolt-On, Cable-In/Cable-Out

Circuit Breaker Type	Circuit Breaker Type Code	Continuous Ampere Rating at 40°C	Number of Poles	Vac	Vdc	Federal Spec. W-C-375b	Interrupting Ratings rms Symmetrical Amperes						Page Number
							Vac Ratings			Vdc Ratings ②③			
							120	120/240	240	24–48	62.5	80	
HQP	P	10–70	1	120/240	24, 48, 62.5	10a, 11a, 12a	—	10,000	—	5000	④	—	**V4-T1-6**
HQP	P	10–125	2	120/240	24, 48, 80	10a, 12a	—	10,000	—	5000	5000	5000	**V4-T1-6**
HQP	P	10–100	2, 3	240	—	10b, 11b, 12b	—	—	10,000	—	—	—	**V4-T1-6**
QPHW	P	15–70	1	120/240	24, 48, 62.5	14a	—	22,000	—	5000	④	—	**V4-T1-6**
QPHW	P	15–125	2	120/240	24, 48, 80	14a	—	22,000	—	5000	5000	5000	**V4-T1-6**
QPHW	P	15–100	2, 3	240	—	14b	—	—	22,000	—	—	—	**V4-T1-6**
QHPX	P	15–70	1	120/240	24, 48, 62.5	—	—	42,000	—	5000	④	—	**V4-T1-7**
QHPX	P	15–100	2	120/240	24, 48, 80	—	—	42,000	—	5000	5000	5000	**V4-T1-7**
QHPX	P	15–100	3	240	—	—	—	—	42,000	—	—	—	**V4-T1-7**
QHPW	P	15–30	1	120/240	24, 48, 62.5	15a	—	65,000	—	5000	④	—	**V4-T1-7**
QHPW	P	15–30	2	120/240	24, 48, 80	15a	—	65,000	—	5000	5000	5000	**V4-T1-7**
QHPW	P	15–20	3	240	—	15b	—	—	65,000	—	—	—	**V4-T1-7**
QPGFT	P, GF	15–40	1	120	—	10a, 11a, 12a	10,000	—	—	—	—	—	**V4-T1-9**
QPGFT	P, GF	15–50	2	120/240	—	10a, 11a, 12a	—	10,000	—	—	—	—	**V4-T1-9**

Notes

① QUICKLAG circuit breakers are suitable for application in relative humidity 0–95% noncondensing.

② Two-pole DC interrupting ratings based on two poles connected in series. Not UL® listed.

③ Breakers at DC ratings are not UL listed.

④ 62.5 Vac interrupting rating is 3800 AIC 10–50A and 2500 AIC 55–100A continuous.

Circuit Breaker Type Codes: **P** Plug-In; **B** Bolt-On; **C** Cable-In/Cable-Out; **GF** Ground Fault, 5 mA; **GFEP** Ground Fault, 30 mA.

For Types GHBS, GBHS and BABRP solenoid-operated, remote-controlled circuit breakers, see **Pages V4-T1-31** to **V4-T1-36**.

Eaton's QUICKLAG Industrial Circuit Breakers ① Plug-In, Bolt-On, Cable-In/Cable-Out, continued

Circuit Breaker Type	Circuit Breaker Type Code	Continuous Ampere Rating at 40°C	Number of Poles	Vac	Vdc	Federal Spec. W-C-375b	Interrupting Ratings rms Symmetrical Amperes						Page Number
							Vac Ratings			Vdc Ratings ②③			
							120	120/240	240	24–48	62.5	80	
QPHGFT	P, GF	15–30	1	120	—	10a, 11a, 12a	22,000	—	—	—	—	—	**V4-T1-9**
QPHGFT	P, GF	15–50	2	120/240	—	10a, 11a, 12a	—	22,000	—	—	—	—	**V4-T1-9**
QPGFEP	P, GFEP	15–40	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-9**
QPGFEP	P, GFEP	15–50	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-9**
QPHGFEP	P, GFEP	15–30	1	120	—	—	22,000	—	—	—	—	—	**V4-T1-9**
BABRSP	B	15–30	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-12**
BABRSP	B	15–30	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-12**
BRRP	P	15–30	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-32**
BRRP	P	15–30	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-32**
CLRP	P	15–30	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-32**
CLRP	P	15–30	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-32**
BAB	B	10–70	1	120/240	24, 48, 62.5	10a, 11a, 12a	—	10,000	—	5000	④	—	**V4-T1-12**
BAB	B	10–125	2	120/240	24, 48, 80	10a, 12a	—	10,000	—	5000	5000	5000	**V4-T1-12**
BAB	B	10–100	2, 3	240	—	10b, 11b, 12b	—	—	10,000	—	—	—	**V4-T1-12**
BABRP	B	15–30	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-32**
BABRP	B	15–30	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-32**
QBAF	B, AF	15–20	1, 2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-15**
QBCAF	B, AF, GF	15–20	1, 2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-15**
QBHW	B	15–70	1	120/240	24, 48, 62.5	14a	—	22,000	—	5000	④	—	**V4-T1-12**
QBHW	B	15–125	2	120/240	24, 48, 80	14a	—	22,000	—	5000	5000	5000	**V4-T1-12**
QBHW	B	15–100	2, 3	240	—	14b	—	—	22,000	—	—	—	**V4-T1-12**
HBAX	B	15–70	1	120/240	24, 48, 62.5	—	—	42,000	—	5000	④	—	**V4-T1-13**
HBAX	B	15–100	2	120/240	24, 48, 80	—	—	42,000	—	5000	5000	5000	**V4-T1-13**
HBAX	B	15–100	3	240		—	—	—	42,000	—	—	—	**V4-T1-13**
HBAW	B	15–30	1	120/240	24, 48, 62.5	15a	—	65,000	—	5000	④	—	**V4-T1-13**
HBAW	B	15–30	2	120/240	24, 48, 80	15a	—	65,000	—	5000	5000	5000	**V4-T1-13**
HBAW	B	15–20	3	240	—	15b	—	—	65,000	—	—	—	**V4-T1-13**
QBGFT	B, GF	15–40	1	120	—	10a, 11a, 12a	10,000	—	—	—	—	—	**V4-T1-18**
QBGFT	B, GF	15–50	2	120/240	—	10a, 11a, 12a	—	10,000	—	—	—	—	**V4-T1-18**
QBHGFT	B, GF	15–30	1	120	—	10a, 11a, 12a	22,000	—	—	—	—	—	**V4-T1-18**
QBHGFT	B, GF	15–30	1	120/240	—	10a, 11a, 12a	—	22,000	—	—	—	—	**V4-T1-18**
QBGFEP	B, GFEP	15–40	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-18**
QBGFEP	B, GFEP	15–50	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-18**
QBHGFEP	B, GFEP	15–30	1	120	—	—	22,000	—	—	—	—	—	**V4-T1-18**
QBHGFEP	B, GFEP	15–30	2	120/240	—	—	22,000	22,000	—	—	—	—	**V4-T1-18**
QC	C	10–70	1	120/240	24, 48, 62.5	10a, 11a, 12a	—	10,000	—	5000	④	—	**V4-T1-41**
QC	C	10–100	2	120/240	24, 48, 80	10a, 12a	—	10,000	—	5000	5000	5000	**V4-T1-41**
QC	C	10–100	2, 3, 4	240	—	10b, 11b, 12b	—	—	10,000	—	—	—	**V4-T1-41**
QCD	C	10–60	1, 2	120/240	24, 48, 62.5	—	10,000	10,000	—	3000	3000	—	**V4-T1-23**
QCD	C	10–100	2, 3	240	24, 48, 62.5	—	—	10,000	—	3000	3000	—	**V4-T1-23**
QCF	C	10–60	1, 2	120/240	24, 48, 62.5	—	10,000	10,000	—	3000	3000	—	**V4-T1-42**

Notes

① QUICKLAG circuit breakers are suitable for application in relative humidity 0–95% noncondensing.

② Two-pole DC interrupting ratings based on two poles connected in series. Not UL listed.

③ Breakers at DC ratings are not UL listed.

④ 62.5 Vac interrupting rating is 3800 AIC 10–50A and 2500 AIC 55–100A continuous.

Circuit Breaker Type Codes: **P** Plug-In; **B** Bolt-On; **C** Cable-In/Cable-Out; **GF** Ground Fault, 5 mA; **GFEP** Ground Fault, 30 mA.

For Types GHBS, GBHS and BABRP solenoid-operated, remote-controlled circuit breakers, see **Pages V4-T1-31** to **V4-T1-36**.

Eaton's QUICKLAG Industrial Circuit Breakers ① Plug-In, Bolt-On, Cable-In/Cable-Out, continued

Circuit Breaker Type	Circuit Breaker Type Code	Continuous Ampere Rating at 40°C	Number of Poles	Vac	Vdc	Federal Spec. W-C-375b	Interrupting Ratings rms Symmetrical Amperes Vac Ratings 120	120/240	240	Vdc Ratings ② 24–48	62.5	80	Page Number
QCF	C	15–20	1, 2	120/240	24, 48, 62.5	—	22,000	—	—	3000	3000	—	**V4-T1-27**
QCF	C	15–30	2, 3	240	24, 48, 62.5	—	—	10,000	—	3000	3000	—	**V4-T1-27**
QCR	C	10–60	1, 2	120/240	24, 48, 62.5	—	10,000	10,000	—	3000	3000	—	**V4-T1-27**
QCR	C	15–20	1, 2	120/240	24, 48, 62.5	—	22,000	—	—	3000	3000	—	**V4-T1-27**
QCR	C	15–30	2, 3	240	24, 48, 62.5	—	—	10,000	—	3000	3000	—	**V4-T1-27**
QCHW	C	15–70	1	120/240	24, 48, 62.5	14a	—	22,000	—	5000	④	—	**V4-T1-22**
QCHW	C	15–100	2	120/240	24, 48, 80	14a	—	22,000	—	5000	5000	5000	**V4-T1-22**
QCHW	C	15–100	2, 3	240	—	14b	—	—	22,000	—	—	—	**V4-T1-22**
QHCX	C	15–70	1	120/240	24, 48, 62.5	—	—	42,000	—	5000	④	—	**V4-T1-22**
QHCX	C	15–100	2	120/240	24, 48, 80	—	—	42,000	—	5000	5000	5000	**V4-T1-22**
QHCX	C	15–100	3	240	—	—	—	—	42,000	—	—	—	**V4-T1-22**
QHCW	C	15–30	1	120/240	24, 48, 62.5	15a	—	65,000	—	5000	③	—	**V4-T1-22**
QHCW	C	15–30	2	120/240	24, 48, 80	15a	—	65,000	—	5000	5000	5000	**V4-T1-22**
QHCW	C	15–20	3	240	—	15b	—	—	65,000	—	—	—	**V4-T1-22**
QCGFT	C, GF	15–40	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-29**
QCGFT	C, GF	15–50	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-29**
QCHGFT	C, GF	15–30	1	120	—	—	22,000	—	—	—	—	—	**V4-T1-29**
QCHGFT	C, GF	15–30	2	120/240	—	—	—	22,000	—	—	—	—	**V4-T1-29**
QCGFEP	C, GFEP	15–40	1	120	—	—	10,000	—	—	—	—	—	**V4-T1-29**
QCGFEP	C, GFEP	15–50	2	120/240	—	—	—	10,000	—	—	—	—	**V4-T1-29**
QCHGFEP	C, GFEP	15–30	1	120	—	—	22,000	—	—	—	—	—	**V4-T1-29**
QCHGFEP	C, GFEP	15–30	2	120/240	—	—	—	22,000	—	—	—	—	**V4-T1-29**

Notes

① QUICKLAG circuit breakers are suitable for application in relative humidity 0–95% noncondensing.

② Two-pole DC interrupting ratings based on two poles connected in series. Not UL listed.

③ 62.5 Vac interrupting rating is 3800 AIC 10–50A and 2500 AIC 55–100A continuous.

Circuit Breaker Type Codes: **P** Plug-In; **B** Bolt-On; **C** Cable-In/Cable-Out; **GF** Ground Fault, 5 mA; **GFEP** Ground Fault, 30 mA.

For Types GHBS, GBHS and BABRP solenoid-operated, remote-controlled circuit breakers, see **Pages V4-T1-31** to **V4-T1-36**.

QUICKLAG Type HQP Single-Pole

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	
Product Selection	**V4-T1-6**
Dimensions	**V4-T1-7**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW

Product Description

- All products 15–100A are HACR rated
- Switching duty rated for 120 Vac fluorescent light applications

Standards and Certifications

- Built and listed to UL 489
- All products UL and CSA® listed

Listed

1 **Product Selection**

QUICKLAG Type HQP Single-Pole

QUICKLAG Type: HQP 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
10	HQP1010	HQP2010	—	HQP3010H ③
15	HQP1015 ①②	HQP2015	HQP2015H	HQP3015H
20	HQP1020 ①②	HQP2020	HQP2020H	HQP3020H
25	HQP1025	HQP2025	HQP2025H	HQP3025H
30	HQP1030	HQP2030	HQP2030H	HQP3030H
35	HQP1035	HQP2035	HQP2035H	HQP3035H
40	HQP1040	HQP2040	HQP2040H	HQP3040H
45	HQP1045	HQP2045	HQP2045H	HQP3045H
50	HQP1050	HQP2050	HQP2050H	HQP3050H
55	HQP1055	HQP2055	HQP2055H	HQP3055H
60	HQP1060	HQP2060	HQP2060H	HQP3060H
70	HQP1070	HQP2070	HQP2070H	HQP3070H
80	—	HQP2080	HQP2080H	HQP3080H
90	—	HQP2090	HQP2090H	HQP3090H
100	HQP1100	HQP2100	HQP2100H	HQP3100H
110	—	HQP2110	—	—
125	—	HQP2125	—	—
150	—	HQP2150	—	—

QUICKLAG Type: HQP Non-Automatic Switches

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
50	HQP1050N	—	HQP2050N	HQP3050N
60	HQP1060N	—	HQP2060N	HQP3060N
100	HQP1100N	—	HQP2100N	HQP3100N

QUICKLAG Type: QPHW 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	QPHW1015 ①	QPHW2015	QPHW2015H	QPHW3015H
20	QPHW1020 ①	QPHW2020	QPHW2020H	QPHW3020H
25	QPHW1025	QPHW2025	QPHW2025H	QPHW3025H
30	QPHW1030	QPHW2030	QPHW2030H	QPHW3030H
35	QPHW1035	QPHW2035	QPHW2035H	QPHW3035H
40	QPHW1040	QPHW2040	QPHW2040H	QPHW3040H
45	QPHW1045	QPHW2045	QPHW2045H	QPHW3045H
50	QPHW1050	QPHW2050	QPHW2050H	QPHW3050H
55	QPHW1055	QPHW2055	QPHW2055H	QPHW3055H
60	QPHW1060	QPHW2060	QPHW2060H	QPHW3060H
70	QPHW1070	QPHW2070	QPHW2070H	QPHW3070H
80	—	QPHW2080	QPHW2080H	QPHW3080H
90	—	QPHW2090	QPHW2090H	QPHW3090H
100	—	QPHW2100	QPHW2100H	QPHW3100H
110	—	QPHW2110	—	—
125	—	QPHW2125	—	—

Notes

① Switching duty rated for 120 Vac fluorescent light applications.

② For special low-magnetic breaker, order **HQP1015L1** or **HQP1020L1**.

③ Not UL listed.

QUICKLAG Type: QHPX 42,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	**QHPX1015** ①	**QHPX2015**	—	**QHPX3015H**
20	**QHPX1020** ①	**QHPX2020**	—	**QHPX3020H**
25	**QHPX1025**	**QHPX2025**	—	**QHPX3025H**
30	**QHPX1030**	**QHPX2030**	—	**QHPX3030H**
35	**QHPX1035**	**QHPX2035**	—	**QHPX3035H**
40	**QHPX1040**	**QHPX2040**	—	**QHPX3040H**
45	**QHPX1045**	**QHPX2045**	—	**QHPX3045H**
50	**QHPX1050**	**QHPX2050**	—	**QHPX3050H**
55	**QHPX1055**	**QHPX2055**	—	**QHPX3055H**
60	**QHPX1060**	**QHPX2060**	—	**QHPX3060H**
70	**QHPX1070**	**QHPX2070**	—	**QHPX3070H**
80	—	**QHPX2080**	—	**QHPX3080H**
90	—	**QHPX2090**	—	**QHPX3090H**
100	—	**QHPX2100**	—	**QHPX3100H**

QUICKLAG Type: QHPW 65,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	**QHPW1015** ①	**QHPW2015**	—	**QHPW3015H**
20	**QHPW1020** ①	**QHPW2020**	—	**QHPW3020H**
25	**QHPW1025**	**QHPW2025**	—	—
30	**QHPW1030**	**QHPW2030**	—	—

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Carton Quantity	Approximate Weight Lbs (kg)	Dimensions
1	24	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
2	12	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
3	8	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)

Note

① Switching duty rated for 120 Vac fluorescent light applications.

1

QUICKLAG Type QPGFT Single-Pole Ground Fault Circuit Breaker

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	
Product Selection	**V4-T1-9**
Wiring Diagram	**V4-T1-10**
Dimensions	**V4-T1-10**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP

Product Description

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- 5 mA trip sensitivity

QUICKLAG Ground Fault Equipment Protectors

- 30 mA trip sensitivity

Standards and Certifications

- Built and listed to UL 489

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- Built and tested to UL 943

QUICKLAG Ground Fault Equipment Protectors

- Built and listed to UL 1053

Listed

Product Selection

QUICKLAG Type QPGFT Single-Pole

Ground Fault Circuit Breakers—5 mA Sensitivity QUICKLAG Type: QPGFT 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QPGFT1015	QPGFT2015
20	QPGFT1020	QPGFT2020
25	QPGFT1025	QPGFT2025
30	QPGFT1030	QPGFT2030
40	QPGFT1040	QPGFT2040
50	—	QPGFT2050

QUICKLAG Type: QPHGFT 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QPHGF1015	QPHGF2015
20	QPHGF1020	QPHGF2020
25	QPHGF1025	QPHGF2025
30	QPHGF1030	QPHGF2030

Ground Fault Equipment Breakers—30 mA Sensitivity QUICKLAG Type: QPGFEP 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QPGFEP1015	QPGFEP2015
20	QPGFEP1020	QPGFEP2020
25	QPGFEP1025	QPGFEP2025
30	QPGFEP1030	QPGFEP2030
40	QPGFEP1040	QPGFEP2040
50	—	QPGFEP2050

QUICKLAG Type: QPHGFEP 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QPHGFEP1015	QPHGFEP2015
20	QPHGFEP1020	QPHGFEP2020
25	QPHGFEP1025	QPHGFEP2025
30	QPHGFEP1030	QPHGFEP2030

Special Application Ground Fault Circuit Protectors—5 mA Sensitivity QUICKLAG Type: QPGFT 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	**QPGFT1015W1**	**QPGFT2015W1**
20	**QPGFT1020W1**	**QPGFT2020W1**
25	**QPGFT1025W1**	**QPGFT2025W1**
30	**QPGFT1030W1**	**QPGFT2030W1**
40	—	**QPGFT2040W1**
50	—	**QPGFT2050W1**
15	**QPGFT1015W2**	—
20	**QPGFT1020W2**	—
25	**QPGFT1025W2**	—
30	**QPGFT1030W2**	—

Special Application Ground Fault Circuit Protectors—30 mA Sensitivity QUICKLAG Type: QPGFEP 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	**QPGFEP1015W1**	**QPGFEP2015W1**
20	**QPGFEP1020W1**	**QPGFEP2020W1**
25	**QPGFEP1025W1**	**QPGFEP2025W1**
30	**QPGFEP1030W1**	**QPGFEP2030W1**
40	—	**QPGFEP2040W1**
50	—	**QPGFEP2050W1**
15	**QPGFEP1015W2**	—
20	**QPGFEP1020W2**	—
25	**QPGFEP1025W2**	—
30	**QPGFEP1030W2**	—

Wiring Diagram

Bell Alarm and Auxiliary Contact Schematic



Single-throw double-pole contacts are UL and CSA listed for 5A at 250 Vac.
Bell Alarm (W1)—contacts change state when breaker trips.
Auxiliary Switch (W2)—contacts change state when breaker is opened (or tripped) or closed.
14-inch (355.6 mm) long 18 AWG pigtail wire leads provided.

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Carton Quantity	Approximate Weight Lbs (kg)	Dimensions
1	24	11.00 (5.0)	12.50 x 6.50 x 5.00 (317.5 x 165.1 x 127.0)
2	5	5.00 (2.3)	15.50 x 6.00 x 4.50 (393.7 x 152.4 x 114.3)

Note

Shipped individually or in carton quantities.

QUICKLAG Type BAB Single-Pole

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	
Product Selection	**V4-T1-12**
Dimensions	**V4-T1-13**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Bolt-On Types BAB, QBHW, HBAX, HBAW

Product Description

- All products 15–100A are HACR rated
- Switching duty rated for 120 Vac fluorescent light applications

Standards and Certifications

- Built and listed to UL 489
- All products UL and CSA listed

Listed

1 **Product Selection**

QUICKLAG Type BAB Single-Pole

QUICKLAG Type: BA 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
10	**BAB1010**	**BAB2010**	**BAB2010H** ③	**BAB3010H** ③
15	**BAB1015** ①②	**BAB2015**	**BAB2015H**	**BAB3015H**
20	**BAB1020** ①②	**BAB2020**	**BAB2020H**	**BAB3020H**
25	**BAB1025**	**BAB2025**	**BAB2025H**	**BAB3025H**
30	**BAB1030**	**BAB2030**	**BAB2030H**	**BAB3030H**
35	**BAB1035**	**BAB2035**	**BAB2035H**	**BAB3035H**
40	**BAB1040**	**BAB2040**	**BAB2040H**	**BAB3040H**
45	**BAB1045**	**BAB2045**	**BAB2045H**	**BAB3045H**
50	**BAB1050**	**BAB2050**	**BAB2050H**	**BAB3050H**
55	**BAB1055**	**BAB2055**	**BAB2055H**	**BAB3055H**
60	**BAB1060**	**BAB2060**	**BAB2060H**	**BAB3060H**
70	**BAB1070**	**BAB2070**	**BAB2070H**	**BAB3070H**
80	—	**BAB2080**	**BAB2080H**	**BAB3080H**
90	—	**BAB2090**	**BAB2090H**	**BAB3090H**
100	**BAB1100**	**BAB2100**	**BAB2100H**	**BAB3100H**
110	—	**BAB2110**	—	—
125	—	**BAB2125**	—	—

QUICKLAG Type: BA Non-Automatic Switches

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
50	**BAB1050N**	—	**BAB2050N**	**BAB3050N**
60	**BAB1060N**	—	**BAB2060N**	**BAB3060N**
100	**BAB1100N**	—	**BAB2100N**	**BAB3100N**

QUICKLAG Type: QBHW 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	**QBHW1015** ①	**QBHW2015**	**QBHW2015H**	**QBHW3015H**
20	**QBHW1020** ①	**QBHW2020**	**QBHW2020H**	**QBHW3020H**
25	**QBHW1025**	**QBHW2025**	**QBHW2025H**	**QBHW3025H**
30	**QBHW1030**	**QBHW2030**	**QBHW2030H**	**QBHW3030H**
35	**QBHW1035**	**QBHW2035**	**QBHW2035H**	**QBHW3035H**
40	**QBHW1040**	**QBHW2040**	**QBHW2040H**	**QBHW3040H**
45	**QBHW1045**	**QBHW2045**	**QBHW2045H**	**QBHW3045H**
50	**QBHW1050**	**QBHW2050**	**QBHW2050H**	**QBHW3050H**
55	**QBHW1055**	**QBHW2055**	**QBHW2055H**	**QBHW3055H**
60	**QBHW1060**	**QBHW2060**	**QBHW2060H**	**QBHW3060H**
70	**QBHW1070**	**QBHW2070**	**QBHW2070H**	**QBHW3070H**
80	—	**QBHW2080**	**QBHW2080H**	**QBHW3080H**
90	—	**QBHW2090**	**QBHW2090H**	**QBHW3090H**
100	—	**QBHW2100**	**QBHW2100H**	**QBHW3100H**
110	—	**QBHW2110**	—	—
125	—	**QBHW2125**	—	—

Notes

① Switching duty rated for 120 Vac fluorescent light applications.

② For special low-magnetic breaker, order **BAB1015L1** or **BAB1020L1**.

③ Not UL listed.

QUICKLAG Type: HBAX 42,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	**HBAX1015** ①	**HBAX2015**	—	**HBAX3015H**
20	**HBAX1020** ①	**HBAX2020**	—	**HBAX3020H**
25	**HBAX1025**	**HBAX2025**	—	**HBAX3025H**
30	**HBAX1030**	**HBAX2030**	—	**HBAX3030H**
35	**HBAX1035**	**HBAX2035**	—	**HBAX3035H**
40	**HBAX1040**	**HBAX2040**	—	**HBAX3040H**
45	**HBAX1045**	**HBAX2045**	—	**HBAX3045H**
50	**HBAX1050**	**HBAX2050**	—	**HBAX3050H**
55	**HBAX1055**	**HBAX2055**	—	**HBAX3055H**
60	**HBAX1060**	**HBAX2060**	—	**HBAX3060H**
70	**HBAX1070**	**HBAX2070**	—	**HBAX3070H**
80	—	**HBAX2080**	—	**HBAX3080H**
80	—	**HBAX2080**	—	**HBAX3080H**
90	—	**HBAX2090**	—	**HBAX3090H**
100	—	**HBAX2100**	—	**HBAX3100H**

QUICKLAG Type: HBAW 65,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
15	**HBAW1015** ①	**HBAW2015**	—	**HBAW3015H**
20	**HBAW1020** ①	**HBAW2020**	—	**HBAW3020H**
25	**HBAW1025**	**HBAW2025**	—	—
30	**HBAW1030**	**HBAW2030**	—	—

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Carton Quantity	Approximate Weight Lbs (kg)	Dimensions
1	24	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
2	12	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
3	8	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)

Note

① Switching duty rated for 120 Vac fluorescent light applications.

1

Bolt-On Arc Fault Circuit Interrupter QUICKLAG Types QBAF, QBCAF

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	
Product Selection	**V4-T1-15**
Wiring Diagrams	**V4-T1-16**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF

Product Description

- All products HACR rated

Features, Benefits and Functions

- 10 and 22 kAIC rating at 120V and 120/240V
- Single-pole AFCI
- HID ratings for HID (High Intensity Discharge) lighting
- All models are HACR rated

Standards and Certifications

- Built and listed to UL 489
- UL File E7819 for QBAF

Listed

Product Selection

QBCAF and QBAF Type AFCIs

Effective immediately, Eaton AFCIs are available for use in Sumter panels with a 22 kAIC rating. This higher rated breaker will allow us to win jobs where AFCIs are specified at higher than 10 kAIC. This breaker provides standard thermal-magnetic protection of branch circuits. This product will have the same form, fit and function of the current bolt-on AFCI (QBCAF and QBAF Type). Product scope is below. These breakers are in Bid Manager™ for Pow-R-Line 1a, Pow-R-Line 1a-LX, Pow-R-Line 3a and Pow-R-Line 4a panelboards. For series rated combinations, continue to use the less expensive 10 kAIC QBCAF and QBAF offerings.

Breakers can also be ordered from Vista.

QBHCAF

1-Inch (25.4 mm) Wide Bolt-On Arc Fault Circuit Interrupter

Poles	kAIC Rating	Ampere Rating	Configuration	Catalog Number
Type QBCAF Combination AFCI				
Single-pole	10 kAIC	15	Combination AFCI	**QBCAF1015**
		20	Combination AFCI	**QBCAF1020**
	22 kAIC	15	Combination AFCI	**QBHCAF1015**
		20	Combination AFCI	**QBHCAF1020**
Type QBAF Branch Feeder AFCI				
Single-pole	10 kAIC	15	Branch Feeder AFCI	**QBAF1015**
		20	Branch Feeder AFCI	**QBAF1020**
	22 kAIC	15	Branch Feeder AFCI	**QBHAF1015**
		20	Branch Feeder AFCI	**QBHAF1020**

1

Wiring Diagrams

Single-Pole 120V Load Application Sourced by 120/240 Vac



Single-Pole Shared Neutral with Multi-Duplex Receptacle Application



QUICKLAG Type QBGFT Single-Pole Ground Fault Circuit Breaker

Contents

Description	*Page*
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	
Product Selection	**V4-T1-18**
Wiring Diagram	**V4-T1-19**
Dimensions	**V4-T1-19**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP

Product Description

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- 5 mA trip sensitivity

QUICKLAG Ground Fault Equipment Protectors

- 30 mA trip sensitivity

Standards and Certifications

- Built and tested to UL 489

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- Built and tested to UL 943

QUICKLAG Ground Fault Equipment Protectors

- Built and tested to UL 1053

Listed

1 **Product Selection**

QUICKLAG Type QBGFT Single-Pole

Ground Fault Circuit Breakers—5 mA Sensitivity QUICKLAG Type: QBGFT 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QBGFT1015	QBGFT2015
20	QBGFT1020	QBGFT2020
25	QBGFT1025	QBGFT2025
30	QBGFT1030	QBGFT2030
40	QBGFT1040	QBGFT2040
50	—	QBGFT2050

QUICKLAG Type: QBHGFT 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QBHGF1015	QBHGF2015
20	QBHGF1020	QBHGF2020
25	QBHGF1025	QBHGF2025
30	QBHGF1030	QBHGF2030

Ground Fault Equipment Breakers—30 mA Sensitivity QUICKLAG Type: QBGFEP 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QBGFEP1015	QBGFEP2015
20	QBGFEP1020	QBGFEP2020
25	QBGFEP1025	QBGFEP2025
30	QBGFEP1030	QBGFEP2030
40	QBGFEP1040	QBGFEP2040
50	—	QBGFEP2050

QUICKLAG Type: QBHGFEP 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	QBHGFEP1015	QBHGFEP2015
20	QBHGFEP1020	QBHGFEP2020
25	QBHGFEP1025	QBHGFEP2025
30	QBHGFEP1030	QBHGFEP2030

Special Application Ground Fault Circuit Protectors—5 mA Sensitivity QUICKLAG Type: QBGFT 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	**QBGFT1015W1**	**QBGFT2015W1**
20	**QBGFT1020W1**	**QBGFT2020W1**
25	**QBGFT1025W1**	**QBGFT2025W1**
30	**QBGFT1030W1**	**QBGFT2030W1**
40	—	**QBGFT2040W1**
50	—	**QBGFT2050W1**
15	**QBGFT1015W2**	—
20	**QBGFT1020W2**	—
25	**QBGFT1025W2**	—
30	**QBGFT1030W2**	—

Special Application Ground Fault Circuit Protectors—30 mA Sensitivity QUICKLAG Type: QBGFEP 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
15	**QBGFEP1015W1**	**QBGFEP2015W1**
20	**QBGFEP1020W1**	**QBGFEP2020W1**
25	**QBGFEP1025W1**	**QBGFEP2025W1**
30	**QBGFEP1030W1**	**QBGFEP2030W1**
40	—	**QBGFEP2040W1**
50	—	**QBGFEP2050W1**
15	**QBGFEP1015W2**	—
20	**QBGFEP1020W2**	—
25	**QBGFEP1025W2**	—
30	**QBGFEP1030W2**	—

Wiring Diagram

Bell Alarm and Auxiliary Contact Schematic

Single-throw double-pole contacts are UL and CSA listed for 5A at 250 Vac.
Bell Alarm (W1)—contacts change state when breaker trips.
Auxiliary Switch (W2)—contacts change state when breaker is opened (or tripped) or closed.
14-inch (355.6 mm) long 18 AWG pigtail wire leads provided.

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Approximate Weight Lbs (kg)	Dimensions
1	11.00 (5.0)	12.50 x 6.50 x 5.00 (317.5 x 165.1 x 127.0)
2	5.00 (2.3)	15.50 x 6.00 x 4.50 (393.7 x 152.4 x 114.3)

Note

Shipped individually or in carton quantities.

1

QUICKLAG Type QC Single-Pole

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	
Product Selection	**V4-T1-21**
Dimensions	**V4-T1-23**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW

Product Description

- All products 10–100A are HACR rated
- Switching duty rated for 120 Vac fluorescent light applications only

Standards and Certifications

- Built and listed to UL 489
- All products UL and CSA listed

Listed

Product Selection

QUICKLAG Type QC Single-Pole

QUICKLAG Type: QC 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number	Four-Pole 240 Vac Catalog Number
5	**QC1005** ①	**QC2005** ①	—	—	—
10	**QC1010**	**QC2010**	**QC2010H** ①	**QC3010H** ①	—
15	**QC1015** ②	**QC2015**	**QC2015H**	**QC3015H**	**QC4015H**
20	**QC1020** ②	**QC2020**	**QC2020H**	**QC3020H**	**QC4020H**
25	**QC1025**	**QC2025**	**QC2025H**	**QC3025H**	**QC4025H**
30	**QC1030**	**QC2030**	**QC2030H**	**QC3030H**	**QC4030H**
35	**QC1035**	**QC2035**	**QC2035H**	**QC3035H**	**QC4035H**
40	**QC1040**	**QC2040**	**QC2040H**	**QC3040H**	**QC4040H**
45	**QC1045**	**QC2045**	**QC2045H**	**QC3045H**	**QC4045H**
50	**QC1050**	**QC2050**	**QC2050H**	**QC3050H**	**QC4050H**
55	**QC1055**	**QC2055**	**QC2055H**	**QC3055H**	**QC4055H**
60	**QC1060**	**QC2060**	**QC2060H**	**QC3060H**	**QC4060H**
70	**QC1070**	**QC2070**	**QC2070H**	**QC3070H**	**QC4070H**
70	—	**QC2080**	**QC2080H**	**QC3080H**	**QC4080H**
90	—	**QC2090**	**QC2090H**	**QC3090H**	**QC4090H**
100	**QC1100**	**QC2100**	**QC2100H**	**QC3100H**	**QC4100H**

QUICKLAG Type: QC Non-Automatic Switches

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number	Four-Pole 240 Vac Catalog Number
50	**QC1050N**	—	**QC2050N**	**QC3050N**	—
60	**QC1060N**	—	**QC2060N**	**QC3060N**	—
100	**QC1100N**	—	**QC2100N**	**QC3100N**	—

Notes

① Not UL listed.

② Switching duty rated for 120 Vac fluorescent light applications only.

For special low-magnetic breaker, order **QC1015L1** or **QC1020L1**.Non-automatic switches, see **Page V4-T1-42**.

QUICKLAG Type: QCHW 22,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number	Four-Pole 240 Vac Catalog Number
15	QCHW1015 ①	QCHW2015	QCHW2015H	QCHW3015H	QCHW4015H
20	QCHW1020 ①	QCHW2020	QCHW2020H	QCHW3020H	QCHW4020H
25	QCHW1025	QCHW2025	QCHW2025H	QCHW3025H	QCHW4025H
30	QCHW1030	QCHW2030	QCHW2030H	QCHW3030H	QCHW4030H
35	QCHW1035	QCHW2035	QCHW2035H	QCHW3035H	QCHW4035H
40	QCHW1040	QCHW2040	QCHW2040H	QCHW3040H	QCHW4040H
45	QCHW1045	QCHW2045	QCHW2045H	QCHW3045H	QCHW4045H
50	QCHW1050	QCHW2050	QCHW2050H	QCHW3050H	QCHW4050H
55	QCHW1055	QCHW2055	QCHW2055H	QCHW3055H	QCHW4055H
60	QCHW1060	QCHW2060	QCHW2060H	QCHW3060H	QCHW4060H
70	QCHW1070	QCHW2070	QCHW2070H	QCHW3070H	QCHW4070H
70	—	QCHW2080	QCHW2080H	QCHW3080H	QCHW4080H
90	—	QCHW2090	QCHW2090H	QCHW3090H	QCHW4090H
100	—	QCHW2100	QCHW2100H	QCHW3100H	QCHW4100H

QUICKLAG Type: QHCX 42,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number	Four-Pole 240 Vac Catalog Number
15	QHCX1015 ①	QHCX2015	—	QHCX3015H	—
20	QHCX1020 ①	QHCX2020	—	QHCX3020H	—
25	QHCX1025	QHCX2025	—	QHCX3025H	—
30	QHCX1030	QHCX2030	—	QHCX3030H	—
35	QHCX1035	QHCX2035	—	QHCX3035H	—
40	QHCX1040	QHCX2040	—	QHCX3040H	—
45	QHCX1045	QHCX2045	—	QHCX3045H	—
50	QHCX1050	QHCX2050	—	QHCX3050H	—
55	QHCX1055	QHCX2055	—	QHCX3055H	—
60	QHCX1060	QHCX2060	—	QHCX3060H	—
70	QHCX1070	QHCX2070	—	QHCX3070H	—
70	—	QHCX2080	—	QHCX3080H	—
90	—	QHCX2090	—	QHCX3090H	—
100	—	QHCX2100	—	QHCX3100H	—

QUICKLAG Type: QHCW 65,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number	Four-Pole 240 Vac Catalog Number
15	QHCW1015 ①	QHCW2015	—	QHCW3015H	—
20	QHCW1020 ①	QHCW2020	—	QHCW3020H	—
25	QHCW1025	QHCW2025	—	—	—
30	QHCW1030	QHCW2030	—	—	—

Notes

① Switching duty rated for 120 Vac fluorescent light applications only.

Non-automatic switches, see **Page V4-T1-42.**

QUICKLAG Type QCD Miniature Circuit Breakers

QCD breakers are used primarily in HVAC and industrial applications.

- Single-, two- and three-pole options
- Modular construction
- DIN mounted (symmetrical rail 35 x 7.5 DIN/EN 50 022)
- QCD same profile as Type QCR
- Flexible power feed connection: wire size, position
- Same breaker size for entire rating range
- Field mountable accessories: finger shroud proof, quick connect terminals
- Other accessories: jumper unit

QUICKLAG Type QCD Miniature Circuit Breaker

QUICKLAG Type QCD 10,000A Interrupting Capacity Thermal-Magnetic Breakers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
10	**QCD1010**	**QCD2010**	—	—
15	**QCD1015**	**QCD2015**	**QCD2015H**	**QCD3015H**
20	**QCD1020**	**QCD2020**	**QCD2020H**	**QCD3020H**
25	**QCD1025**	**QCD2025**	**QCD2025H**	**QCD3025H**
30	**QCD1030**	**QCD2030**	**QCD2030H**	**QCD3030H**
35	**QCD1035**	**QCD2035**	**QCD2035H**	**QCD3035H**
40	**QCD1040**	**QCD2040**	**QCD2040H**	**QCD3040H**
45	**QCD1045**	**QCD2045**	**QCD2045H**	**QCD3045H**
50	**QCD1050**	**QCD2050**	**QCD2050H**	**QCD3050H**
55	**QCD1055**	**QCD2055**	**QCD2055H**	**QCD3055H**
60	**QCD1060**	**QCD2060**	**QCD2060H**	**QCD3060H**
70	—	**QCD2070**	**QCD2070H**	**QCD3070H**
80	—	**QCD2080**	**QCD2080H**	**QCD3080H**
90	—	**QCD2090**	**QCD2090H**	**QCD3090H**
100	—	**QCD2090**	**QCD2090H**	**QCD3100H**
	—	**QCD2100**	**QCD2100H**	—

QUICKLAG Type QCD Non-Automatic Switches

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
60	—	—	**QCD2060NA**	—
100	—	—	—	—

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Carton Quantity	Approximate Weight Lbs (kg)	Dimensions
1	24	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
2	12	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
3	8	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)

1

Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH

Single-Pole *Two-Pole* *Single-Pole* *Two-Pole*

QCR (Rear-Mounted Breakers) *QCF (Front-Mounted Breakers)*

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	
Product Selection	**V4-T1-25**
QCR and QCF Options and Accessories	**V4-T1-27**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH

Product Description

Eaton Type QCR circuit breakers have as a standard feature provisions for 35 mm DIN rail rear mounting with a spring-loaded release. Optional clips for individual mounting are available as a separate accessory.

Type QCF have two threaded steel inserts to facilitate front mounting with #6–32 steel screws. The clamp type terminals are accessible from the rear of the breaker so that cables can be accessed without removal of the breaker from the front cover.

Application Description

QCR and QCF circuit breakers are only 1/2-inch (12.7 mm) wide per pole and are excellent for general purpose industrial applications where space savings is required.

Features, Benefits and Functions

- 1/2-inch (12.7 mm) wide per pole
- Cable-in/cable-out
- Black cases with black handles
- Three position handle: ON, Tripped (center), OFF
- Thermal-magnetic protection

Standards and Certifications

- Built and listed to UL 489
- UL File No. E7819
- CSA File No. LR48907
- Type QCR and QCF circuit breakers are UL listed circuit breakers that are suitable for use as branch circuit protectors
- All ratings 15–60A are HACR rated

Listed

Product Selection

Cable-In/Cable-Out, 1/2-Inch Wide

QCR Breaker Catalog Numbers ①②③④

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac ⑤ Catalog Number	Three-Pole Catalog Number
QCR Breaker 10 kAIC Interrupting Ratings				
10	**QCR1010**	**QCR2010**	—	—
	QCR1010T	**QCR2010T**	—	—
	—	**QCR2010P**	—	—
15	**QCR1015** ⑥	**QCR2015**	**QCR2015H**	**QCR3015H**
	QCR1015T ⑥	**QCR2015T**	**QCR2015HT**	**QCR3015HT**
	—	**QCR2015P**	—	—
20	**QCR1020** ⑥	**QCR2020**	**QCR2020H**	**QCR3020H**
	QCR1020T ⑥	**QCR2020T**	**QCR2020HT**	**QCR3020HT**
	—	**QCR2020P**	—	—
25	**QCR1025**	**QCR2025**	**QCR2025H**	**QCR3025H**
	QCR1025T	**QCR2025T**	**QCR2025HT**	**QCR3025HT**
	—	**QCR2025P**	—	—
30	**QCR1030**	**QCR2030**	**QCR2030H**	**QCR3030H**
	QCR1030T	**QCR2030T**	**QCR2030HT**	**QCR3030HT**
	—	**QCR2030P**	—	—
35	**QCR1035**	**QCR2035**	—	—
	—	**QCR2035P**	—	—
40	**QCR1040**	**QCR2040**	—	—
	—	**QCR2040P**	—	—
45	**QCR1045**	**QCR2045**	—	—
	—	**QCR2045P**	—	—
50	**QCR1050**	**QCR2050**	—	—
	—	**QCR2050P**	—	—
55	**QCR1055**	**QCR2055**	—	—
	—	**QCR2055P**	—	—
60 ⑦	**QCR1060**	**QCR2060**	—	—
	—	**QCR2060P**	—	—
QCR Breaker 22 kAIC Interrupting Ratings				
15	**QCRH1015** ⑥	**QCRH2015**	—	—
	QCRH1015T ⑥	**QCRH2015T**	—	—
20	**QCRH1020** ⑥	**QCRH2020**	—	—
	QCRH1020T ⑥	**QCRH2020T**	—	—

Notes

① Standard breaker terminals are box type lugs.

② Breakers with **T** Catalog Number Suffix are suitable for line and load side ring terminal connection (#10–32 plus/minus terminal screw provided).

③ Breakers with **P** Catalog Number Suffix are suitable for terminating two 10 AWG Quick-Connect Type Terminals per phase on breaker load side.

④ Breakers with Shunt Trip (extra pole required on breaker right-hand side) are available on single-, two- and three-pole. Contact the Customer Support Center at 1-800-356-1243.

⑤ Breakers with **H** Catalog Suffix have 240 Vac construction.

⑥ All 15 and 20A single-pole breakers are SWD (Switching Duty) rated for fluorescent lighting applications.

⑦ 60/75°C Cu/Al wire on all ratings except 60A, which requires Cu only conductor.

1

Cable-In/Cable-Out, 1/2-Inch Wide

QCF Breaker Catalog Numbers ①②③

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac ④ Catalog Number	Three-Pole Catalog Number
QCF Breaker 10 kAIC Interrupting Ratings				
10	**QCF1010**	**QCF2010**	—	—
	QCF1010T	**QCF2010T**	—	—
15	**QCF1015** ⑤	**QCF2015**	**QCF2015H**	**QCF3015H**
	QCF1015T ⑤	**QCF2015T**	**QCF2015HT**	**QCF3015HT**
20	**QCF1020** ⑤	**QCF2020**	**QCF2020H**	**QCF3020H**
	QCF1020T ⑤	**QCF2020T**	**QCF2020HT**	**QCF3020HT**
25	**QCF1025**	**QCF2025**	**QCF2025H**	**QCF3025H**
	QCF1025T	**QCF2025T**	**QCF2025HT**	**QCF3025HT**
30	**QCF1030**	**QCF2030**	**QCF2030H**	**QCF3030H**
	QCF1030T	**QCF2030T**	**QCF2030HT**	**QCF3030HT**
35	**QCF1035**	**QCF2035**	—	—
40	**QCF1040**	**QCF2040**	—	—
45	**QCF1045**	**QCF2045**	—	—
50	**QCF1050**	**QCF2050**	—	—
55	**QCF1055**	**QCF2055**	—	—
60 ⑥	**QCF1060**	**QCF2060**	—	—
QCF Breaker 22 kAIC Interrupting Ratings				
15	**QCFH1015** ⑤	**QCFH2015**	—	—
	QCFH1015T ⑤	**QCFH2015T**	—	—
20	**QCFH1020** ⑤	**QCFH2020**	—	—
	QCFH1020T ⑤	**QCFH2020T**	—	—

Notes

① Standard breaker terminals are box type lugs.

② Breakers with **T** Catalog Number Suffix are suitable for line and load side ring terminal connection (#10–32 plus/minus terminal screw provided).

③ Breakers with Shunt Trip Attachment (extra pole required on breaker right-hand side) are available. Contact the Customer Support Center.

④ Breakers with **H** Catalog Suffix have 240 Vac construction.

⑤ All 15 and 20A single-pole breakers are SWD (Switching Duty) rated for fluorescent lighting applications.

⑥ 60/75°C Cu/Al wire on all ratings except 60A, which requires Cu only conductor.

QCR and QCF Options and Accessories

QCR and QCF Standard Box Terminals

Factory-installed line and load side breaker terminal to accommodate14 AWG to 4 AWG wire.

Standard Box Terminals



QCR Quick-Connect Terminals

Factory-installed two-prong quick-connect terminal on breaker load side suitable for terminating two 10 AWG wire with insulated slip-on terminals as shown. Line side terminal is the standard type.

Catalog Suffix "P"

QCR and QCF Ring or Spade Lug Terminals (10 to 30A Ratings Only)

Factory-installed line and load side terminals each equipped with a #10–32 screw suitable for terminating one 10 AWG wire with insulated ring or spade type terminal as shown.

Catalog Suffix "T"



Available QCR and QCF Breaker Accessories

Description	Catalog Number
Steel mounting clip mounts QCR breaker if individual mounting is required. Quantity two required for single- and two-pole and four required for three-pole breakers.	**QCRMTGFT**
Removable padlock device for single-pole QCR or QCF breaker.	**QCRFPL1P**
Removable padlock device for multi-pole QCR or QCF breaker.	**QCRFPLMP**
Padlock bracket assembly for QCR or QCF single- or multi-pole breakers (OFF only).	**QCRFLOFF**
Padlock bracket for QCR, lock-off only.	**QCRPLOFF**

Technical Data and Specifications

- Single-, two- and three-pole
- 10 kAIC at 120/240 Vac, 10–60A
- 22 kAIC at 120/240 Vac, 15–20A
- 10 kAIC at 240 Vac, 10–30A
- 3 kAIC at 62.5 Vdc (single-pole)
- 3 kAIC at 130 Vdc (two poles in series)
- Normal operating environment:
  - 0–40°C
  - 5–95% humidity (noncondensing)

1

QUICKLAG Type QCGFT Single-Pole Ground Fault Circuit Breaker

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	
Product Selection	**V4-T1-29**
Wiring Diagram	**V4-T1-30**
Dimensions	**V4-T1-30**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP

Product Description

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- 5 mA trip sensitivity

QUICKLAG Ground Fault Equipment Protectors

- 30 mA trip sensitivity

Standards and Certifications

QUICKLAG Ground Fault Circuit Breakers, Class A GFCI

- Built and tested to UL 943

QUICKLAG Ground Fault Equipment Protectors

- Built and tested to UL 1053

Listed

Product Selection

QUICKLAG Type QCGFT Single-Pole Ground Fault Circuit Breaker

Breaker Catalog Numbers

Continuous Ampere Rating at 40°C	Single-Pole 120 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number
Ground Fault Circuit Breakers—5 mA Sensitivity QUICKLAG Type: QCGFT 10,000A Interrupting Capacity Thermal-Magnetic Breakers		
15	QCGFT1015	QCGFT2015
20	QCGFT1020	QCGFT2020
25	QCGFT1025	QCGFT2025
30	QCGFT1030	QCGFT2030
40	QCGFT1040	QCGFT2040
50	—	QCGFT2050
QUICKLAG Type: QCHGFT 22,000A Interrupting Capacity Thermal-Magnetic Breakers		
15	QCHGFT1015	QCHGFT2015
20	QCHGFT1020	QCHGFT2020
25	QCHGFT1025	QCHGFT2025
30	QCHGFT1030	QCHGFT2030
Ground Fault Equipment Protectors—30 mA Sensitivity QUICKLAG Type: QCGFEP 10,000A Interrupting Capacity Thermal-Magnetic Breakers		
15	QCGFEP1015	QCGFEP2015
20	QCGFEP1020	QCGFEP2020
25	QCGFEP1025	QCGFEP2025
30	QCGFEP1030	QCGFEP2030
40	QCGFEP1040	QCGFEP2040
50	—	QCGFEP2050
QUICKLAG Type: QCHGFEP 22,000A Interrupting Capacity Thermal-Magnetic Breakers		
15	QCHGFEP1015	QCHGFEP2015
20	QCHGFEP1020	QCHGFEP2020
25	QCHGFEP1025	QCHGFEP2025
30	QCHGFEP1030	QCHGFEP2030
Special Application Ground Fault Circuit Protector—5 mA Sensitivity QUICKLAG Type: QCGFT 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)		
15	QCGFT1015W1	QCGFT2015W1
20	QCGFT1020W1	QCGFT2020W1
25	QCGFT1025W1	QCGFT2025W1
30	QCGFT1030W1	QCGFT2030W1
40	—	QCGFT2040W1
50	—	QCGFT2050W1
15	QCGFT1015W2	—
20	QCGFT1020W2	—
25	QCGFT1025W2	—
30	QCGFT1030W2	—
Special Application Ground Fault Equipment Protectors—30 mA Sensitivity QUICKLAG Type: QCGFEP 10,000A Interrupting Capacity with Bell Alarm (W1) or Auxiliary Switch (W2)		
15	QCGFEP1015W1	QCGFEP2015W1
20	QCGFEP1020W1	QCGFEP2020W1
25	QCGFEP1025W1	QCGFEP2025W1
30	QCGFEP1030W1	QCGFEP2030W1
40	—	QCGFEP2040W1
50	—	QCGFEP2050W1
15	QCGFEP1015W2	—
20	QCGFEP1020W2	—
25	QCGFEP1025W2	—
30	QCGFEP1030W2	—

1

Wiring Diagram

Bell Alarm and Auxiliary Contact Schematic



Single-throw double-pole contacts are UL and CSA listed for 5A at 250 Vac.
Bell Alarm (W1)—contacts change state when breaker trips.
Auxiliary Switch (W2)—contacts change state when breaker is opened (or tripped) or closed.
14-inch (355.6 mm) long 18 AWG pigtail wire leads provided.

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Number of Poles	Carton Quantity	Approximate Weight Lbs (kg)	Dimensions
1	20	11.00 (5.0)	12.50 x 6.50 x 5.00 (317.5 x 165.1 x 127.0)
2	5	5.00 (2.3)	15.50 x 6.00 x 4.50 (393.7 x 152.4 x 114.3)

BABRP and BABRSP Breakers—Single- and Two-Pole

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	
Product Selection	**V4-T1-32**
Technical Data and Specifications	**V4-T1-33**
Wiring Diagrams	**V4-T1-33**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP

Product Description

The BABRP and BABRSP are bolt-on branch circuit breakers designed for use in panelboards. The BRRP is a plug-on branch circuit breaker designed for use in load-centers not manufactured with breakers with a 1-inch wide format and are listed on the "Compatibility list for Classified Applications"—Pub. 26271. In addition to providing conventional branch circuit protection, they include a unique solenoid-operated mechanism that provides for efficient breaker pulse-on and pulse-off operation when used with a suitable controller like Eaton's Pow-R-Command™ lighting control system. These breakers can also be controlled by pushbutton or a PLC unit.

Application Description

Eaton's BABRP, BABRSP, BRRP and CLRP breakers are remotely operated molded case circuit breakers ideally suited for lighting control applications or energy management applications.

Features, Benefits and Functions

- Bolt-on line-side terminal (BABRP, BABRSP—Type BA)
- Plug-on line-side terminal (BRRP—Type BR, CLRP—Type CL)
- Cable connected load-side terminal
- Four-position control terminal
- Bi-metal assembly for thermal overload protection
- Fast-acting short-circuit protection
- Arc-chute assembly for fast-acting arc extinction
- Three-position handle: OFF, TRIP (Center), ON
- Handle permits manual switching when control power is lost
- Mechanical trip indicator
- 15 and 20A breakers SWD (switching duty) rated
- HID ratings for HID (high intensity discharge) lighting
- All models HACR rated
- Status feedback of control circuit (BABRSP)
- Series rated (BABRP, BABRSP only)
  - BRRP series rated same as BR breakers
  - BABRP, BABRSP same as BA breakers

QUICKLAG Type QCGFT Single-Pole Ground Fault Circuit Breaker

BABRP UL 489 and CSA 22.2 Interrupting Ratings

Number of Poles	Ampere Rating ①	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	120/240	277/480	Catalog Number
1	15	10,000	—	—	**BABRP1015**
	20	10,000	—	—	**BABRP1020**
	25	10,000	—	—	**BABRP1025**
	30	10,000	—	—	**BABRP1030**
2	15	—	10,000	—	**BABRP2015**
	20	—	10,000	—	**BABRP2020**
	25	—	10,000	—	**BABRP2025**
	30	—	10,000	—	**BABRP2030**

BABRP and BABRSP Wire Harness

Description	Catalog Number
This 60-inch (1524.0 mm) wire pigtail provides a connection from a single BABRP's control plug to a customer's pushbutton, relay or PLC. Each box contains 12 pigtails. Wires are 22 AWG, 600V. Order in multiples of 12.	**SLBKRPTL1**

BABRSP UL 489 and CSA 22.2 Interrupting Ratings

Number of Poles	Ampere Rating ①	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	120/240	277/480	Catalog Number
1	15	10,000	—	—	**BABRSP1015**
	20	10,000	—	—	**BABRSP1020**
	25	10,000	—	—	**BABRSP1025**
	30	10,000	—	—	**BABRSP1030**
2	15	—	10,000	—	**BABRSP2015**
	20	—	10,000	—	**BABRSP2020**
	25	—	10,000	—	**BABRSP2025**
	30	—	10,000	—	**BABRSP2030**

BRRP UL 489 and CSA 22.2 Interrupting Ratings

Number of Poles	Ampere Rating	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	120/240	Catalog Number
1	15	10,000	—	**BRRP115**
	20	10,000	—	**BRRP120**
	25	10,000	—	**BRRP125**
	30	10,000	—	**BRRP130**
2	15	—	10,000	**BRRP215**
	20	—	10,000	**BRRP220**
	25	—	10,000	**BRRP225**
	30	—	10,000	**BRRP230**

CLRP UL 489 and CSA 22.2 Interrupting Ratings

Number of Poles	Ampere Rating	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	120/240	Catalog Number
1	15	10,000	—	**CLRP115**
	20	10,000	—	**CLRP120**
	25	10,000	—	**CLRP125**
	30	10,000	—	**CLRP130**
2	15	—	10,000	**CLRP215**
	20	—	10,000	**CLRP220**
	25	—	10,000	**CLRP225**
	30	—	10,000	**CLRP230**

Note

① Continuous current rating at 40°C.

Technical Data and Specifications

Solenoid Operating Data

- Power requirements: 24 Vac/dc (20.4V minimum–30V maximum)
  - Controlled signal: +AC/DC 8 ms minimum with zero cross, 300 ms maximum
  - AC: 1.3 cycles minimum, 18 cycles or 300 ms maximum
  - DC: 8 ms minimum, 300 ms maximum
  - Maximum duty cycle of 6 OPEN/CLOSE cycles per minute
- Current draw: open 1A, close 3/4A
- Blue wire: power input (see power requirements)
- Black wire: remote opening
- Red wire: remote closing
- Yellow wire: feedback status from power input, maximum 0.50A draw (BABRSP only)

Operation

- Tripping system—the BABRP, BABRSP, BRRP and CLRP circuit breakers have a permanent trip unit that contains a factory preset thermal (overload) trip element in each pole
- Operating mechanism—the BABRP, BABRSP, BRRP and CLRP circuit breakers have an over-center toggle mechanism that provides quick-make, quick-break operation. The operating mechanism is trip free. An internal cross-bar provides a common tripping of all multi-pole circuit breakers

Operating/Application Data

- Ambient temperature: 0 to 40°C
- Nominal pulse magnitude: 24 Vac/dc
- Frequency: 50/60 Hz
- Maximum breaker cycling: 6 operations per minute
- Tolerance: +10% to –15% of nominal voltage
- Humidity: 0 to 95% noncondensing

Wiring Diagrams

Control Circuit for the BABRP and BABRSP



GHBS and GHQRSP

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	
Product Selection	**V4-T1-35**
Technical Data and Specifications	**V4-T1-36**
Wiring Diagrams	**V4-T1-36**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

Solenoid Operator—Remote-Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers

Product Description

Eaton's GHBS, GBHS and GHQRSP circuit breakers are bolt-on branch circuit breakers designed for use in 277/480 Vac panelboards. In addition to providing conventional branch circuit protection, they include a unique solenoid-operated mechanism that provides for efficient breaker pulse-on and pulse-off operation when used with a suitable controller like Eaton's Pow-R-Command lighting control system.

Features, Benefits and Functions

- Bolt-on line-side terminal
- Cable-connected load-side terminal
- Status switch—remote status and breaker status available from internal auxiliary switches
- Bi-metal assembly for thermal overload protection
- Fast-acting short-circuit protection
- Arc-runner and arc-chute assembly for fast-acting arc extinction
- Three-position breaker handle: OFF, TRIP (Center), ON
- Visual indication of the remotely operated contact's position (open, closed or trip)
- Remote override handle permits manual switching when control power is lost
- 15 and 20A breakers SWD (switching duty) rated.
- 15 and 20A breakers HID rated for HID (High intensity discharge) lighting
- All models HACR rated
- Series rated with various Eaton main circuit breakers

Product Selection

GHBS—Single-Pole

GHBS UL 489 Interrupting Ratings

Number of Poles	Ampere Rating ①	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	240	277/480	Catalog Number
1	15	65,000	—	14,000	**GHBS1015D**
	20	65,000	—	14,000	**GHBS1020D**
	30	65,000	—	14,000	**GHBS1030D**
2	15	—	65,000	14,000	**GHBS2015D**
	20	—	65,000	14,000	**GHBS2020D**
	30	—	65,000	14,000	**GHBS2030D**

GBHS CSA 22.2 Interrupting Ratings (Not UL Listed)

Number of Poles	Ampere Rating ①	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 347/600	Catalog Number
1	15	10,000	**GBHS1015D**
	20	10,000	**GBHS1020D**
2	15	10,000	**GBHS2015D**
	20	10,000	**GBHS2020D**

GHQRSP UL 489 and CSA 22.2 Interrupting Ratings

Number of Poles	Ampere Rating ①	Interrupting Capacity (Symmetrical Amperes) Vac (50/60 Hz) 120	120/240	277	480Y/277	Catalog Number ②
1	15	65,000	65,000	14,000	14,000	**GHQRSP1015**
	20	65,000	65,000	14,000	14,000	**GHQRSP1020**
	30	65,000	65,000	14,000	14,000	**GHQRSP1030**
2	15	65,000	65,000	14,000	14,000	**GHQRSP2015**
	20	65,000	65,000	14,000	14,000	**GHQRSP2020**
	30	65,000	65,000	14,000	14,000	**GHQRSP2030**

Notes

① Continuous current rating at 40°C.

② All UL listed circuit breakers are HID (high intensity discharge) rated.

Technical Data and Specifications

Solenoid Operating Data

- Power requirements: 24 Vac/dc (20.4V minimum–30V maximum)
  - Controlled signal: +AC/DC 8 ms minimum with zero cross, 300 ms maximum
  - AC: 1.3 cycles minimum, 18 cycles or 300 ms maximum
  - DC: 8 ms minimum, 300 ms maximum
  - Maximum duty cycle of 6 OPEN/CLOSE cycles per minute
- Current draw: open 1A, close 3/4A
- Blue wire: power input (see power requirements)
- Black wire: remote opening
- Red wire: remote closing
- Yellow wire: feedback status from power input, maximum 0.50A draw

Operation

Mechanism manually operated by external handle allowing ON, OFF and RESET operation. Handle assumes a center TRIP position after performing protective response.

Operating/Application Data

- Ambient temperature: 0–40°C
- Frequency: 48–62 Hz
- Humidity: 0–95% noncondensing

Terminal Type

Circuit Breaker Type	Circuit Breaker Amperes	Screw Head Type	Terminal Type	Range
GHQRSP	15–20	Slotted	Clamp	#14–#4 AWG

Wiring Diagrams

Typical Single-Pole Circuit Breaker Schematic Diagram for GHBS and GBHS Breakers



Typical Single-Pole Circuit Breaker Schematic Diagram for GHQRSP Breakers



Dimensions

Approximate Dimensions in Inches (mm)

Dimensions per Pole

Circuit Breaker Type	Width	Height ②	Length ③
GHQRSP	1.00 (25.4)	4.63 (117.6)	2.81 (71.4)

Notes

① Purchase separate AMP Inc. conductor plug #640426-3.
② Excluding line terminal.
③ Excluding handle.

International Rated

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	
Product Selection	**V4-T1-38**
Technical Data and Specifications	**V4-T1-39**
Dimensions	**V4-T1-39**
Special Application Breakers, Types HQP, BA, QC	**V4-T1-40**

International Rated Types HQP, BA, QC, GFMB, GFXBC

Product Description

QUICKLAG International Circuit Breakers

- Bolt-on Type BA

QUICKLAG International Ground Fault Circuit Breakers

- Plug-on Type GFMB
- Cable-in/cable-out Type GFXBC

Standards and Certifications

QUICKLAG International Circuit Breakers

- Built and test certified to BS3871, Pt. 1
- 50/60 Hz, 40°C

QUICKLAG International Ground Fault Circuit Breakers

- Built and test certified to BS3871, Pt. 1; BS3871, Section 31-C; BS4293
- 50/60 Hz, 40°C; 30 mA sensitivity

1

Product Selection

BAB

Breaker Catalog Numbers

Continuous Ampere Rating at 40°C	Single-Pole 240/415 Vac Catalog Number	Two-Pole 240/415 Vac Catalog Number	Three-Pole 240/415 Vac Catalog Number
3000A Interrupting Capacity (M3) Bolt-On Thermal-Magnetic Circuit Breakers			
10	**BAB1010E**	**BAB2010E**	**BAB3010E**
15	**BAB1015E**	**BAB2015E**	**BAB3015E**
16	—	—	—
20	**BAB1020E**	**BAB2020E**	**BAB3020E**
25	**BAB1025E**	**BAB2025E**	**BAB3025E**
30	**BAB1030E**	**BAB2030E**	**BAB3030E**
32	—	—	—
40	**BAB1040E**	**BAB2040E**	**BAB3040E**
50	**BAB1050E**	**BAB2050E**	**BAB3050E**
60	**BAB1060E**	**BAB2060E**	**BAB3060E**
70	**BAB1070E**	**BAB2070E**	**BAB3070E**
90	—	**BAB2090E**	**BAB3090E**
100	—	**BAB2100E**	**BAB3100E**
6000A Interrupting Capacity (M6) Bolt-On Thermal-Magnetic Circuit Breakers			
15	**BAB1015HE**	**BAB2015HE**	**BAB3015HE**
20	**BAB1020HE**	**BAB2020HE**	**BAB3020HE**
25	**BAB1025HE**	**BAB2025HE**	**BAB3025HE**
30	**BAB1030HE**	**BAB2030HE**	**BAB3030HE**
40	**BAB1040HE**	**BAB2040HE**	**BAB3040HE**
50	**BAB1050HE**	**BAB2050HE**	**BAB3050HE**
60	**BAB1060HE**	**BAB2060HE**	**BAB3060HE**
70	**BAB1070HE**	**BAB2070HE**	**BAB3070HE**
90	—	**BAB2090HE**	**BAB3090HE**
100	—	**BAB2100HE**	**BAB3100HE**

Breaker Catalog Numbers—Ground Fault Single-Pole 30 mA Sensitivity

Continuous Ampere Rating at 40°C	240/415 Vac Catalog Number
3000A Interrupting Capacity (M3) Plug-On Thermal-Magnetic Circuit Breakers	
10	**GFMB110B2**
15	**GFMB115B2**
16	**GFMB116B2**
20	**GFMB120B2**
25	**GFMB125B2**
30	**GFMB130B2**
32	**GFMB132B2**
40	**GFMB140B2**

Note

For other 240/415V applications, please contact the Customer Support Center at 1-800-356-1243.

Technical Data and Specifications

Interrupting Ratings

Ratings	Suffix E	Suffix HE
International Circuit Breakers		
NEMA® 120/240 Vac	10,000 AIC	10,000 AIC
BS3871 220/380, 240/415 Vac	3000 AIC	6000 AIC
International Ground Fault Circuit Breakers		
BS3871 220/380, 240/415 Vac	3000 AIC	

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Miniature Circuit Breaker	Number of Poles	Standard Carton Quantity	Approximate Carton Weight Lbs (kg)	Approximate Standard Carton
QUICKLAG Type B	1	24	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
	2	12	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
	3	8	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
QUICKLAG Ground Fault				
Type P—All	1	20	11.00 (5.0)	12.50 x 6.50 x 5.00 (317.5 x 165.1 x 127.0)
Types B and C—All	1	20	11.00 (5.0)	12.50 x 7.00 x 5.50 (317.5 x 177.8 x 139.7)
Types P and B—All	2	5	5.00 (2.3)	12.50 x 6.00 x 4.50 (317.5 x 152.4 x 114.3)

1

QUICKLAG Type P Switching Neutral

Contents

Description	*Page*
Quick Reference	**V4-T1-2**
QUICKLAG Plug-On Types HQP, QPHW, QHPX, QHPW	**V4-T1-5**
QUICKLAG Plug-On Ground Fault and Equipment Protectors, Types QPGFT, QPHGFT, QPGFEP, QPHGFEP	**V4-T1-8**
Bolt-On Types BAB, QBHW, HBAX, HBAW	**V4-T1-11**
Bolt-On Arc Fault Circuit Interrupter Types QBAF, QBCAF	**V4-T1-14**
Bolt-On Ground Fault and Equipment Protectors, Types QBGFT, QBHGFT, QBGFEP, QBHGFEP	**V4-T1-17**
Cable-In/Cable-Out Types QC, QCD, QCHW, QHCX, QHCW	**V4-T1-20**
Cable-In/Cable-Out, 1/2-Inch Wide, Types QCR, QCF, QCRH, QCFH	**V4-T1-24**
Cable-In/Cable-Out Ground Fault and Equipment Protectors, Types QCGFT, QCHGFT, QCGFEP, QCHGFEP	**V4-T1-28**
Solenoid-Operated, Remote-Controlled Latching Types BABRP, BABRSP, BRRP and CLRP	**V4-T1-31**
Solenoid Operator—Remote Controlled Latching for Type GHBS, GBHS and GHQRSP Breakers	**V4-T1-34**
International Rated Types HQP, BA, QC, GFMB, GFXBC	**V4-T1-37**
Special Application Breakers, Types HQP, BA, QC	
Product Selection	**V4-T1-41**
Accessories	**V4-T1-43**
Factory Modifications and Installed Terminals	**V4-T1-46**
Technical Data and Specifications	**V4-T1-47**
Dimensions	**V4-T1-48**

Special Application Breakers, Types HQP, BA, QC

Product Description

Breakers

- Plug-on Type HQP: 10–30A, single- and two-pole, 10 kAIC
- Bolt-on Type BA: 10–30A, single- and two-pole, 10 kAIC
- Cable-in Type QC: 10–30A, single- and two-pole, 10 kAIC

Switching neutral QUICKLAG breakers available in single- and two-pole configurations, plus neutral pole for applications in accordance with NEC® 514.5, 240.22 and 380.2. A single-pole device takes two pole spaces, and a two-pole device takes three pole spaces.

QUICKLAG HID (High Intensity Discharge) Breakers

- Plug-on Type HQP: 15–60A, single- and two-pole, 10 kAIC
- Bolt-on Type BA: 15–60A, single- and two-pole, 10 kAIC
- Cable-in Type QC: 15–60A, single- and two-pole, 10 kAIC

Breakers designed specifically for use with high intensity discharge (HID) lighting applications. (UL listed as standard lighting breakers.)

Molded Case Switches—Non-automatic QUICKLAG Molded Case Switch

- Plug-on Type HQP: 50, 60,100A, single-, two- and three-pole
- Bolt-on Type BA: 50, 60,100A, single-, two- and three-pole
- Cable-in Type QC: 50, 60,100A, single-, two- and three-pole

Standards and Certifications

- All products UL and CSA listed

Listed

Product Selection

QUICKLAG Type P Switching Neutral

Breaker Catalog Numbers

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
QUICKLAG Type: HQP Switching Neutral Thermal-Magnetic Breakers				
10	**HQP2010B**	**HQP3010B**	—	—
15	**HQP2015B**	**HQP3015B**	—	—
20	**HQP2020B**	**HQP3020B**	—	—
25	**HQP2025B**	**HQP3025B**	—	—
30	**HQP2030B**	**HQP3030B**	—	—
QUICKLAG Type: BA Switching Neutral Thermal-Magnetic Breakers				
10	**BAB2010C**	**BAB3010C**	—	—
15	**BAB2015C**	**BAB3015C**	—	—
20	**BAB2020C**	**BAB3020C**	—	—
25	**BAB2025C**	**BAB3025C**	—	—
30	**BAB2030C**	**BAB3030C**	—	—
QUICKLAG Type: QC Switching Neutral Thermal-Magnetic Breakers				
10	**QC2010B**	**QC3010B**	—	—
15	**QC2015B**	**QC3015B**	—	—
20	**QC2020B**	**QC3020B**	—	—
25	**QC2025B**	**QC3025B**	—	—
30	**QC2030B**	**QC3030B**	—	—
QUICKLAG Type: HQP HID (High Intensity Discharge) Thermal-Magnetic Breakers				
15	**HQP1015D**	**HQP2015D**	—	—
20	**HQP1020D**	**HQP2020D**	—	—
25	**HQP1025D**	**HQP2025D**	—	—
30	**HQP1030D**	**HQP2030D**	—	—
35	**HQP1035D**	**HQP2035D**	—	—
40	**HQP1040D**	**HQP2040D**	—	—
50	**HQP1050D**	**HQP2050D**	—	—
60	**HQP1060D**	**HQP2060D**	—	—
QUICKLAG Type: BA HID (High Intensity Discharge) Thermal-Magnetic Breakers				
15	**BAB1015D**	**BAB2015D**	—	—
20	**BAB1020D**	**BAB2020D**	—	—
25	**BAB1025D**	**BAB2025D**	—	—
30	**BAB1030D**	**BAB2030D**	—	—
35	**BAB1035D**	**BAB2035D**	—	—
40	**BAB1040D**	**BAB2040D**	—	—
50	**BAB1050D**	**BAB2050D**	—	—
60	**BAB1060D**	**BAB2060D**	—	—
QUICKLAG Type: QC HID (High Intensity Discharge) Thermal-Magnetic Breakers				
15	**QC1015D**	**QC2015D**	—	—
20	**QC1020D**	**QC2020D**	—	—
25	**QC1025D**	**QC2025D**	—	—
30	**QC1030D**	**QC2030D**	—	—
35	**QC1035D**	**QC2035D**	—	—
40	**QC1040D**	**QC2040D**	—	—
50	**QC1050D**	**QC2050D**	—	—
60	**QC1060D**	**QC2060D**	—	—

Breaker Catalog Numbers, continued

Continuous Ampere Rating at 40°C	Single-Pole 120/240 Vac Catalog Number	Two-Pole 120/240 Vac Catalog Number	Two-Pole 240 Vac Catalog Number	Three-Pole 240 Vac Catalog Number
QUICKLAG Type: HQP Non-Automatic Switches				
50	**HQP1050N**	—	**HQP2050N**	**HQP3050N**
60	**HQP1060N**	—	**HQP2060N**	**HQP3060N**
100	**HQP1100N**	—	**HQP2100N**	**HQP3100N**
QUICKLAG Type: BA Non-Automatic Switches				
50	**BAB1050N**	—	**BAB2050N**	**BAB3050N**
60	**BAB1060N**	—	**BAB2060N**	**BAB3060N**
100	**BAB1100N**	—	**BAB2100N**	**BAB3100N**
QUICKLAG Type: QC Non-Automatic Switches				
50	**QC1050N**	—	**QC2050N**	**QC3050N**
60	**QC1060N**	—	**QC2060N**	**QC3060N**
100	**QC1100N**	—	**QC2100N**	**QC3100N**
QUICKLAG Type: QCD Non-Automatic Switches				
60	—	—	**QCD2060NA**	—
100	—	—	—	—

Accessories ①

Handle Locks: Non-Padlockable ②

	Description	Order in Multiples of	Catalog Number
QL1NPL	QUICKLAG Type P, B, C—single-pole	10	**QL1NPL**
QL23NPL	QUICKLAG Type P, B, C—two- and three-pole	10	**QL23NPL**

Handle Locks: Padlockable ②

	Description	Order in Multiples of	Catalog Number
QL1PL	QUICKLAG Type P, B, C—single-pole	10	**QL1PL**
QL123PL	QUICKLAG Type P, B and ground fault—single-, two- and three-pole	10	**QL123PL**
QC123PL	QUICKLAG Type C —single-, two- and three-pole	10	**QC123PL**
	QUICKLAG Type P, B—single-, two- and three-pole (off only)	10	**QL123PLOFF**
	QUICKLAG Type C—single-, two- and three-pole (off only)	10	**QC123PLOFF**

Notes

① See **Page V4-T1-27** for QCR and QCF accessories.

② Can lock in ON or OFF position.

Mounting Hardware

	Description	Order in Multiples of	Catalog Number
QCFCLIP	QUICKLAG Type C face mounting clip	24	**QCFCLIP**
QC1FP	QUICKLAG Type C face mounting plate—single-pole	10	**QC1FP**
QC2FP	QUICKLAG Type C face mounting plate—two-pole	10	**QC2FP**
QC3FP	QUICKLAG Type C face mounting plate—three-pole	10	**QC3FP**
	QUICKLAG Type C face mounting plate and lock-off (off only)—two-pole ①	10	**QC2FPLOFF**
	QUICKLAG Type C face mounting plate and lock-off (off only)—three-pole	10	**QC3FPLOFF**
QCBCLIP	QUICKLAG Type C base mounting clamp	10	**QCBCLIP**
QC6BP	QUICKLAG Type mounting plate—six poles total	10	**QC6BP**

Note

① Suitable for ground fault breakers.

Mounting Hardware, continued

Description	Order in Multiples of	Catalog Number
QUICKLAG Type C base mounting plate—six poles total—heavy-duty screw-secured	10	**QC6BPS**
QUICKLAG Type C (QCD) 2-way jumper unit with cover	10	**QCDJ2**
QUICKLAG Type C (QCD) 4-way jumper unit with cover	10	**QCDJ4**
QUICKLAG Type C (QCD) 6-way jumper unit with cover	10	**QCDJ6**
QUICKLAG Type C (QCD) 2-way jumper unit, no cover	10	**QCDJ2T**
QUICKLAG Type C (QCD) 4-way jumper unit, no cover	10	**QCDJ4T**
QUICKLAG Type C (QCD) 6-way jumper unit, no cover	10	**QCDJ6T**
QUICKLAG Type QCD Finger protection attachment	10	**QCDFP**
QUICKLAG Type QCD 4-prong Quick Connect	10	**QCDQUICK**
QUICKLAG Type C DIN rail adapter	6	**QCDINADAPT**
QUICKLAG Type QCD ring lug attachment	10	**QCDRING**

QCDJ4



QCDINADAPT

QCDRING

Dummy Breakers

Description	Order in Multiples of	Catalog Number
QUICKLAG Type P	1	**HQP1000**
QUICKLAG Type B	1	**BAB1000**
QUICKLAG Type C	1	**QC1000**
QUICKLAG Type C clear choice breaker	4	**QC30SAMPLE**

Miscellaneous

Description	Order in Multiples of	Catalog Number
QUICKLAG Type C Spacer	1	**QCRSPACER**

QCRSPACER

Handle Tie

Description	Order in Multiples of	Catalog Number
QUICKLAG handle tie—single-pole	100	**QL1HT**

QL1HT

1

Factory Modifications and Installed Terminals

Factory Modifications ①

Type of Modification	Breaker Type	Catalog Suffix
Shunt trip (requires one extra pole space on right side) 120, 208, 240 Vac Draws 2.6A at 120V, draws 11A at 24 Vdc	QUICKLAG Types P, B and C	**S**
Shunt trip (requires one extra pole space on right side) 24, 48 Vac/dc Draws 2.6A at 120V, draws 11A at 24 Vdc	QUICKLAG Types P, B and C	**S1**
Special calibration (50°C) (no UL)	QUICKLAG Types P, B and C	**V**
Shock testing	QUICKLAG Types P, B and C	**L**
Freeze testing	QUICKLAG Types P, B and C	**Y**
Moisture-fungus treatment	QUICKLAG Types P, B, C and ground fault	**F**
Marine duty	QUICKLAG Types P, B, C	**H08**
Naval duty	QUICKLAG Types P, B, C	**H09**
400 Hz calibration	QUICKLAG Types P, B, C	**G**
Specific DC ratings (breaker marked with a max. Vdc rating)	QUICKLAG Types P, B, C	**Q thru Q9** ②

Spare Terminal Hardware Screws (Lugs not Included)

Terminal Type	Description	Order in Multiples of	Catalog Number
1	QUICKLAG terminal screw	10	**QLLDTSA**
2	QUICKLAG terminal screw	10	**QLLDTSB**
3	QUICKLAG terminal screw	10	**QLLDTSC**
5	QUICKLAG binding head terminal screw and clamp	10	**QLBHTSE**
6 and 7	QUICKLAG terminal screw	10	**QLLNTSFG**

Notes

① Contact Eaton for factory modifications available for QCR and QCF breakers.

② Q = 32 Vdc; Q1 = 32–40 Vdc; Q2 = 37.5 Vdc; Q3 = 45 Vdc; Q4 = 48 Vdc; Q5 = 50 Vdc; Q6 = 62.5 Vdc; Q7 = 75 Vdc (2P); Q8 = 80 Vdc (2P); Q9 = 125 Vdc (QCR 2P); Q10 = 62.5 Vdc (QCR 1P).

Technical Data and Specifications

Factory-Installed Breaker Terminals

Breaker Type	Continuous Ampere Rating	Standard Line Terminal			Standard Load Terminal			Optional Terminals	
		Terminal Type	Wire Type	Wire Range (AWG)	Terminal Type	Wire Type	Wire Range (AWG)	Line	Load
QUICKLAG Type P HQP, QPHW, QHPX, QHPW	10–30	Plug-on female clips that mate with the bus stabs			1	Cu/Al	14–4	N/A	3
	35–50				2	Cu/Al	14–4	N/A	3
	55–125				3	Cu/Al	8–1/0	N/A	—
QUICKLAG ground fault QPGFT, QPGFEP, QPHGFT, QPHGFEP	10–40	Plug-on female clips that mate with the bus stabs			1 (single-pole)	Cu/Al	14–4	N/A	3
	10–40				1	Cu/Al	—	N/A	3
	10–30				1	Cu	14–8	N/A	—
QUICKLAG Type B BAB, QBHW, HBAX, HBAW	10–40	Extended tangs that bolt directly to the bus			1 (single- and two-pole)	Cu/Al	14–4	N/A	3
	35–50				2 (three-pole)	Cu/Al	14–4	N/A	3
	55–125				3	Cu/Al	8–1/0	N/A	—
QUICKLAG ground fault QBGFT, QBGFEP, QBHGFEP, QBHGFT	10–40	Extended tangs that bolt directly to the bus			1 (single-pole)	Cu/Al	14–4	N/A	N/A
	10–40				1	Cu/Al	14–8	N/A	N/A
	10–30				1	Cu	14–8	N/A	N/A
QUICKLAG Type C QC, QCHW, QHCX, QHCW	10–20	5	Cu/Al	TBD	5	Cu/Al	14–10	6, 7	6, 7, 8
	25–60	6	Cu/Al	TBD	2	Cu/Al	14–4	5, 7	5, 6, 7, 8
	70–100	7	Cu/Al	TBD	3	Cu/Al	8–1/0	5	5, 7, 8
QUICKLAG QCR, QCF	10–55	1	Cu/Al	TBD	1	Cu/Al	14–4	N/A	N/A
	60	1	Cu	TBD	1	Cu	14–4	N/A	N/A
QUICKLAG ground fault QCGFT, QCGFEP, QCHGFT, QCHGFEP	10–20	6	Cu/Al	TBD	14–8	Cu/Al	14–4	6, 7	5
	25–50	6	Cu/Al	TBD	1	Cu/Al	14–4	5, 7	5
	10–30	6	—	—	—	—	—	—	—
QUICKLAG QCD	10–60	9	Cu/Al	14–4	9	Cu/Al	14–4	See Accessories	
	70–100	10	Cu	4–1/0	10	Cu	4–1/0	See Accessories	

1

Steel Box Lug

2

Steel Box Lug

3

Steel Box Lug

5

Steel Ring Type

6

Aluminum Box Lug

7

Aluminum Box Lug

8

4-Prong Quick Connect

9

QCD Terminal Assembly 10–60A

10

QCD Terminal Assembly 70–100A

Note

① Clamp on line side only.

1

Dimensions

Approximate Dimensions in Inches (mm)

Shipping Data

Miniature Circuit Breaker	Number of Poles	Standard Carton Quantity	Approximate Carton Weight Lbs (kg)	Approximate Standard Carton
QUICKLAG Types B, P, C–all	1	24	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
QUICKLAG Types B, P, C–all	2	12	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
QUICKLAG Types B, P, C–all	3	8	9.00 (4.1)	12.50 x 7.50 x 5.00 (317.5 x 190.5 x 127.0)
QUICKLAG ground fault Type P–all	1	20	11.00 (5.0)	12.50 x 6.50 x 5.00 (317.5 x 165.1 x 127.0)
Types B and C–all	1	20	11.00 (5.0)	12.50 x 7.00 x 5.50 (317.5 x 177.8 x 139.7)
Types P and B–all	2	5	5.00 (2.3)	12.50 x 6.00 x 4.50 (317.5 x 152.4 x 114.3)

FAZ-NA and FAZ-NA-L Circuit Breakers

Optimum and Efficient Protection for Every Application

Contents

Description	*Page*
FAZ-NA and FAZ-NA-L Circuit Breakers	
Catalog Number Selection	**V4-T1-50**
Product Selection	**V4-T1-51**
Accessories	**V4-T1-58**
Technical Data and Specifications	**V4-T1-62**
Dimensions	**V4-T1-68**

FAZ-NA and FAZ-NA-L Circuit Breakers

Product Overview

Optimum product quality, tested reliability and safety stand for best protection of personnel, installations and plant. Eaton's FAZ-NA and FAZ-NA-L DIN rail mountable circuit breakers are designed for use in branch service applications.

Powerful Offering for Machine and System Builders

FAZ-NA and FAZ-NA-L are available with B, C and D characteristics in accordance with UL® 489, CSA® C22.2 No.5; UL 1077, CSA C22.2 No.235 and IEC 60947-2. These devices are CE marked.

Application Description

Feeder and branch circuit protection for:

- Convenience receptacle circuits (internal/external)
- Motor control circuits
- Load circuits leaving the equipment (external)
- HACR internal/external equipment (heating, air conditioning, refrigeration)
- PLC I/O points
- Computers
- Power supplies
- Control instrumentation
- Relays
- UPS
- Power conditioners

Features

- Complete range of UL 489 listed DIN rail mounted miniature circuit breakers up to 40A current rating
- Two distinct UL 489 FAZ-NA offerings available to provide the best solution for the application—FAZ-NA at 277/480 Vac and FAZ-NA-L at 240 Vac
- Standard ratings of 10 kAIC available at both 240 Vac and 277/480 Vac
- Select amperages available at 14 kAIC for both the 240 Vac and 277/480 Vac offerings and 10 kAIC up to 125 Vdc per pole
- Current limiting design provides fast short-circuit interruption that reduces the let-through energy, which can damage the circuit
- Suitable for branch circuit device protection
- Thermal-magnetic overcurrent protection
  - Three levels of short-circuit protection, categorized by B, C and D curves
- Trip-free design—breaker can not be defeated by holding the handle in the ON position
- Captive screws cannot be lost
- SWD (switching duty)—suitable for switching fluorescent lighting loads ($I_n \leq 20A$)
- Fulfill UL 489, CSA C22.2 No.5 and also IEC 60947-2 Standard
- For use in applications for which UL 1077 or CSA C22.2 No.235 are also allowed
- Field-installable shunt trip and auxiliary switch subsequent mounting
- Separate version for ring-tongue connection (Type FAZ-RT), terminal screws can be removed (on both sides)
- Module width of only 17.7 mm (per pole)
- Contact Position Indicator (red/green)
- Easy installation on DIN rail
- Possibility for sealing the toggle in ON or OFF position

Device Printing on Front and Side

Installation options

These branch circuit breakers are available in two terminal configurations: standard box terminals that accept multiple conductors and ring-tongue terminals, ideally suited to demanding requirements of the semi-conductor industry. All breakers mount on standard 35 mm DIN rail. Bus connectors and feeder terminal facilitate mounting and wiring of multiple miniature circuit breaker arrays in control panel assemblies. These circuit breakers can also be reverse feed.

1

Standards and Certifications

FAZ-NA

FAZ-NA complies with the latest national and international standards.

- UL 489
  - Standard for molded case circuit breakers (MCCB) for feeder and branch circuit protection
  - Products meet the requirements of the National Electrical Code® (NEC®)
- CSA C22.2 No.5
  - Standard for molded case circuit breakers (MCCB) for feeder and branch circuit protection (corresponds closely to UL 489 Standard)
  - Products meet the requirements of the Canadian Electrical Code (CEC)
- RoHS compliant
- VDE compliant
- ABS compliant

Listed

FAZ-NA-L

FAZ-NA-L 0.5–32 A at 240 Vac comply with the following standards.

- UL 489 listed
- CSA C22.2 No. 5-02
- IEC rated
- RoHS compliant

Listed

Catalog Number Selection

FAZ - C 6 / 1 - NA - SP

Breaker Family
FAZ = FAZ UL circuit breaker

Trip Characteristics ①
B = 3–5X I_n
C = 5–10X I_n
D = 10–20X I_n

Ampere Rating ②			
0.5	= 0.5A	**10**	= 10A
1	= 1A	**13**	= 13A
1.5	= 1.5A	**15**	= 15A
2	= 2A	**16**	= 16A
3	= 3A	**20**	= 20A
4	= 4A	**25**	= 25A
5	= 5A	**30**	= 30A
6	= 6A	**32**	= 32A
7	= 7A	**35**	= 32A
8	= 8A	**40**	= 40A

Number of Poles
1 = Single-pole
2 = Two-pole
3 = Three-pole

Terminal	
NA	= UL 489 branch circuit at 277/480 Vac with screw terminals
RT	= UL 489 branch circuit at 277/480 Vac with ring-tongue terminals
DC	= UL 489 branch circuit at 125 Vdc per pole
NA-L	= UL 489 branch circuit at 240 Vac with screw terminals
RT-L	= UL 489 branch circuit at 240 Vac with ring-tongue terminals

Single Package ③	
SP	= Single package for C and D curve single-pole at 277 Vac only
Blank	= Standard packaging

Notes

① I_n = Rated current for instantaneous trip characteristics.

② B curve starts at 1 ampere.

③ Single package only available for 277 Vac offering—not an option for 240 Vac line.

Product Selection

FAZ-NA B Curve 277/480 Vac Rated Offering

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC B Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
B Curve (3–5X I_n Current Rating)			
1	**FAZ-B1/1-NA**	**FAZ-B1/2-NA**	**FAZ-B1/3-NA**
1.5	**FAZ-B1.5/1-NA**	**FAZ-B1.5/2-NA**	**FAZ-B1.5/3-NA**
2	**FAZ-B2/1-NA**	**FAZ-B2/2-NA**	**FAZ-B2/3-NA**
3	**FAZ-B3/1-NA**	**FAZ-B3/2-NA**	**FAZ-B3/3-NA**
4	**FAZ-B4/1-NA**	**FAZ-B4/2-NA**	**FAZ-B4/3-NA**
5	**FAZ-B5/1-NA**	**FAZ-B5/2-NA**	**FAZ-B5/3-NA**
6	**FAZ-B6/1-NA**	**FAZ-B6/2-NA**	**FAZ-B6/3-NA**
7	**FAZ-B7/1-NA**	**FAZ-B7/2-NA**	**FAZ-B7/3-NA**
8	**FAZ-B8/1-NA**	**FAZ-B8/2-NA**	**FAZ-B8/3-NA**
10	**FAZ-B10/1-NA**	**FAZ-B10/2-NA**	**FAZ-B10/3-NA**
13	**FAZ-B13/1-NA**	**FAZ-B13/2-NA**	**FAZ-B13/3-NA**
15	**FAZ-B15/1-NA**	**FAZ-B15/2-NA**	**FAZ-B15/3-NA**
16	**FAZ-B16/1-NA**	**FAZ-B16/2-NA**	**FAZ-B16/3-NA**
20	**FAZ-B20/1-NA**	**FAZ-B20/2-NA**	**FAZ-B20/3-NA**
25	**FAZ-B25/1-NA**	**FAZ-B25/2-NA**	**FAZ-B25/3-NA**
30	**FAZ-B30/1-NA**	**FAZ-B30/2-NA**	**FAZ-B30/3-NA**
32	**FAZ-B32/1-NA**	**FAZ-B32/2-NA**	**FAZ-B32/3-NA**

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC B Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
B Curve with Ring-Tongue Terminals (3–5X I_n Current Rating)			
1	**FAZ-B1/1-RT**	**FAZ-B1/2-RT**	**FAZ-B1/3-RT**
1.5	**FAZ-B1.5/1-RT**	**FAZ-B1.5/2-RT**	**FAZ-B1.5/3-RT**
2	**FAZ-B2/1-RT**	**FAZ-B2/2-RT**	**FAZ-B2/3-RT**
3	**FAZ-B3/1-RT**	**FAZ-B3/2-RT**	**FAZ-B3/3-RT**
4	**FAZ-B4/1-RT**	**FAZ-B4/2-RT**	**FAZ-B4/3-RT**
5	**FAZ-B5/1-RT**	**FAZ-B5/2-RT**	**FAZ-B5/3-RT**
6	**FAZ-B6/1-RT**	**FAZ-B6/2-RT**	**FAZ-B6/3-RT**
7	**FAZ-B7/1-RT**	**FAZ-B7/2-RT**	**FAZ-B7/3-RT**
8	**FAZ-B8/1-RT**	**FAZ-B8/2-RT**	**FAZ-B8/3-RT**
10	**FAZ-B10/1-RT**	**FAZ-B10/2-RT**	**FAZ-B10/3-RT**
13	**FAZ-B13/1-RT**	**FAZ-B13/2-RT**	**FAZ-B13/3-RT**
15	**FAZ-B15/1-RT**	**FAZ-B15/2-RT**	**FAZ-B15/3-RT**
16	**FAZ-B16/1-RT**	**FAZ-B16/2-RT**	**FAZ-B16/3-RT**
20	**FAZ-B20/1-RT**	**FAZ-B20/2-RT**	**FAZ-B20/3-RT**
25	**FAZ-B25/1-RT**	**FAZ-B25/2-RT**	**FAZ-B25/3-RT**
30	**FAZ-B30/1-RT**	**FAZ-B30/2-RT**	**FAZ-B30/3-RT**
32	**FAZ-B32/1-RT**	**FAZ-B32/2-RT**	**FAZ-B32/3-RT**

Note

① Two-piece order. Quantities of two per box.

FAZ-NA C Curve 277/480 Vac Rated Offering

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC C Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
C Curve (5–10X I_n Current Rating)			
0.5	FAZ-C0.5/1-NA-SP	FAZ-C0.5/2-NA	FAZ-C0.5/3-NA
1	FAZ-C1/1-NA-SP	FAZ-C1/2-NA	FAZ-C1/3-NA
1.5	FAZ-C1.5/1-NA-SP	FAZ-C1.5/2-NA	FAZ-C1.5/3-NA
2	FAZ-C2/1-NA-SP	FAZ-C2/2-NA	FAZ-C2/3-NA
3	FAZ-C3/1-NA-SP	FAZ-C3/2-NA	FAZ-C3/3-NA
4	FAZ-C4/1-NA-SP	FAZ-C4/2-NA	FAZ-C4/3-NA
5	FAZ-C5/1-NA-SP	FAZ-C5/2-NA	FAZ-C5/3-NA
6	FAZ-C6/1-NA-SP	FAZ-C6/2-NA	FAZ-C6/3-NA
7	FAZ-C7/1-NA-SP	FAZ-C7/2-NA	FAZ-C7/3-NA
8	FAZ-C8/1-NA-SP	FAZ-C8/2-NA	FAZ-C8/3-NA
10	FAZ-C10/1-NA-SP	FAZ-C10/2-NA	FAZ-C10/3-NA
13	FAZ-C13/1-NA-SP	FAZ-C13/2-NA	FAZ-C13/3-NA
15	FAZ-C15/1-NA-SP	FAZ-C15/2-NA	FAZ-C15/3-NA
16	FAZ-C16/1-NA-SP	FAZ-C16/2-NA	FAZ-C16/3-NA
20	FAZ-C20/1-NA-SP	FAZ-C20/2-NA	FAZ-C20/3-NA
25	FAZ-C25/1-NA-SP	FAZ-C25/2-NA	FAZ-C25/3-NA
30	FAZ-C30/1-NA-SP	FAZ-C30/2-NA	FAZ-C30/3-NA
32	FAZ-C32/1-NA-SP	FAZ-C32/2-NA	FAZ-C32/3-NA

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC C Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
C Curve with Ring-Tongue Terminals (5–10X I_n Current Rating)			
0.5	FAZ-C0.5/1-RT-SP	FAZ-C0.5/2-RT	FAZ-C0.5/3-RT
1	FAZ-C1/1-RT-SP	FAZ-C1/2-RT	FAZ-C1/3-RT
1.5	FAZ-C1.5/1-RT-SP	FAZ-C1.5/2-RT	FAZ-C1.5/3-RT
2	FAZ-C2/1-RT-SP	FAZ-C2/2-RT	FAZ-C2/3-RT
3	FAZ-C3/1-RT-SP	FAZ-C3/2-RT	FAZ-C3/3-RT
4	FAZ-C4/1-RT-SP	FAZ-C4/2-RT	FAZ-C4/3-RT
5	FAZ-C5/1-RT-SP	FAZ-C5/2-RT	FAZ-C5/3-RT
6	FAZ-C6/1-RT-SP	FAZ-C6/2-RT	FAZ-C6/3-RT
7	FAZ-C7/1-RT-SP	FAZ-C7/2-RT	FAZ-C7/3-RT
8	FAZ-C8/1-RT-SP	FAZ-C8/2-RT	FAZ-C8/3-RT
10	FAZ-C10/1-RT-SP	FAZ-C10/2-RT	FAZ-C10/3-RT
13	FAZ-C13/1-RT-SP	FAZ-C13/2-RT	FAZ-C13/3-RT
15	FAZ-C15/1-RT-SP	FAZ-C15/2-RT	FAZ-C15/3-RT
16	FAZ-C16/1-RT-SP	FAZ-C16/2-RT	FAZ-C16/3-RT
20	FAZ-C20/1-RT-SP	FAZ-C20/2-RT	FAZ-C20/3-RT
25	FAZ-C25/1-RT-SP	FAZ-C25/2-RT	FAZ-C25/3-RT
30	FAZ-C30/1-RT-SP	FAZ-C30/2-RT	FAZ-C30/3-RT
32	FAZ-C32/1-RT-SP	FAZ-C32/2-RT	FAZ-C32/3-RT

Note

① Option for single packaging on single-pole C and D curves only; add suffix SP when ordering.

FAZ-NA D Curve 277/480 Vac Rated Offering

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC D Curve (13–20A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
D Curve (10–20X I_n Current Rating)			
0.5	**FAZ-D0.5/1-NA-SP**	**FAZ-D0.5/2-NA**	**FAZ-D0.5/3-NA**
1	**FAZ-D1/1-NA-SP**	**FAZ-D1/2-NA**	**FAZ-D1/3-NA**
1.5	**FAZ-D1.5/1-NA-SP**	**FAZ-D1.5/2-NA**	**FAZ-D1.5/3-NA**
2	**FAZ-D2/1-NA-SP**	**FAZ-D2/2-NA**	**FAZ-D2/3-NA**
3	**FAZ-D3/1-NA-SP**	**FAZ-D3/2-NA**	**FAZ-D3/3-NA**
4	**FAZ-D4/1-NA-SP**	**FAZ-D4/2-NA**	**FAZ-D4/3-NA**
5	**FAZ-D5/1-NA-SP**	**FAZ-D5/2-NA**	**FAZ-D5/3-NA**
6	**FAZ-D6/1-NA-SP**	**FAZ-D6/2-NA**	**FAZ-D6/3-NA**
7	**FAZ-D7/1-NA-SP**	**FAZ-D7/2-NA**	**FAZ-D7/3-NA**
8	**FAZ-D8/1-NA-SP**	**FAZ-D8/2-NA**	**FAZ-D8/3-NA**
10	**FAZ-D10/1-NA-SP**	**FAZ-D10/2-NA**	**FAZ-D10/3-NA**
13	**FAZ-D13/1-NA-SP**	**FAZ-D13/2-NA**	**FAZ-D13/3-NA**
15	**FAZ-D15/1-NA-SP**	**FAZ-D15/2-NA**	**FAZ-D15/3-NA**
16	**FAZ-D16/1-NA-SP**	**FAZ-D16/2-NA**	**FAZ-D16/3-NA**
20	**FAZ-D20/1-NA-SP**	**FAZ-D20/2-NA**	**FAZ-D20/3-NA**
25	**FAZ-D25/1-NA-SP**	**FAZ-D25/2-NA**	**FAZ-D25/3-NA**
30	**FAZ-D30/1-NA-SP**	**FAZ-D30/2-NA**	**FAZ-D30/3-NA**
32	**FAZ-D32/1-NA-SP**	**FAZ-D32/2-NA**	**FAZ-D32/3-NA**

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC D Curve (13–20A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
D Curve with Ring-Tongue Terminals (10–20X I_n Current Rating)			
0.5	**FAZ-D0.5/1-RT-SP**	**FAZ-D0.5/2-RT**	**FAZ-D0.5/3-RT**
1	**FAZ-D1/1-RT-SP**	**FAZ-D1/2-RT**	**FAZ-D1/3-RT**
1.5	**FAZ-D1.5/1-RT-SP**	**FAZ-D1.5/2-RT**	**FAZ-D1.5/3-RT**
2	**FAZ-D2/1-RT-SP**	**FAZ-D2/2-RT**	**FAZ-D2/3-RT**
3	**FAZ-D3/1-RT-SP**	**FAZ-D3/2-RT**	**FAZ-D3/3-RT**
4	**FAZ-D4/1-RT-SP**	**FAZ-D4/2-RT**	**FAZ-D4/3-RT**
5	**FAZ-D5/1-RT-SP**	**FAZ-D5/2-RT**	**FAZ-D5/3-RT**
6	**FAZ-D6/1-RT-SP**	**FAZ-D6/2-RT**	**FAZ-D6/3-RT**
7	**FAZ-D7/1-RT-SP**	**FAZ-D7/2-RT**	**FAZ-D7/3-RT**
8	**FAZ-D8/1-RT-SP**	**FAZ-D8/2-RT**	**FAZ-D8/3-RT**
10	**FAZ-D10/1-RT-SP**	**FAZ-D10/2-RT**	**FAZ-D10/3-RT**
13	**FAZ-D13/1-RT-SP**	**FAZ-D13/2-RT**	**FAZ-D13/3-RT**
15	**FAZ-D15/1-RT-SP**	**FAZ-D15/2-RT**	**FAZ-D15/3-RT**
16	**FAZ-D16/1-RT-SP**	**FAZ-D16/2-RT**	**FAZ-D16/3-RT**
20	**FAZ-D20/1-RT-SP**	**FAZ-D20/2-RT**	**FAZ-D20/3-RT**
25	**FAZ-D25/1-RT-SP**	**FAZ-D25/2-RT**	**FAZ-D25/3-RT**
30	**FAZ-D30/1-RT-SP**	**FAZ-D30/2-RT**	**FAZ-D30/3-RT**
32	**FAZ-D32/1-RT-SP**	**FAZ-D32/2-RT**	**FAZ-D32/3-RT**

Note

① Option for single packaging on single-pole C and D curves only; add suffix SP when ordering.

1

FAZ-NA-DC C Curve at 125 Vdc per Pole Offering

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as Branch Circuit Breakers
- Interrupting capacity: 10 kA at 125 Vdc UL/CSA, 10 kA at 250 Vdc
- 125 Vdc for one-pole, 250 Vdc for two-pole in series
- Current limiting device
- Polarity (+/–) sensitive and not for use on photovoltaic string application
- UL file number E235139



Single-Pole

Two-Pole

FAZ-NA-DC UL 489 Circuit Breakers— 10 kAIC at 125 Vdc Per Pole

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number
C Curve (5–10X I_n Current Rating)		
2	**FAZ-C2/1-NA-DC-SP**	**FAZ-C2/2-NA-DC**
3	**FAZ-C3/1-NA-DC-SP**	**FAZ-C3/2-NA-DC**
4	**FAZ-C4/1-NA-DC-SP**	**FAZ-C4/2-NA-DC**
5	**FAZ-C5/1-NA-DC-SP**	**FAZ-C5/2-NA-DC**
6	**FAZ-C6/1-NA-DC-SP**	**FAZ-C6/2-NA-DC**
7	**FAZ-C7/1-NA-DC-SP**	**FAZ-C7/2-NA-DC**
8	**FAZ-C8/1-NA-DC-SP**	**FAZ-C8/2-NA-DC**
10	**FAZ-C10/1-NA-DC-SP**	**FAZ-C10/2-NA-DC**
13	**FAZ-C13/1-NA-DC-SP**	**FAZ-C13/2-NA-DC**
15	**FAZ-C15/1-NA-DC-SP**	**FAZ-C15/2-NA-DC**
16	**FAZ-C16/1-NA-DC-SP**	**FAZ-C16/2-NA-DC**
20	**FAZ-C20/1-NA-DC-SP**	**FAZ-C20/2-NA-DC**
25	**FAZ-C25/1-NA-DC-SP**	**FAZ-C25/2-NA-DC**
30	**FAZ-C30/1-NA-DC-SP**	**FAZ-C30/2-NA-DC**
32	**FAZ-C32/1-NA-DC-SP**	**FAZ-C32/2-NA-DC**
35	**FAZ-C35/1-NA-DC-SP**	**FAZ-C35/2-NA-DC**
40	**FAZ-C40/1-NA-DC-SP**	**FAZ-C40/2-NA-DC**

Note

① Option for single packaging on single-pole C curves only; add suffix SP when ordering.

FAZ-NA UL 489 Circuit Breakers at 240 Vac—10 kAIC B Curve

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC B Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
B Curve (3–5X I_n Current Rating)			
1	FAZ-B1/1-NA-L	FAZ-B1/2-NA-L	FAZ-B1/3-NA-L
1.5	FAZ-B1.5/1-NA-L	FAZ-B1.5/2-NA-L	FAZ-B1.5/3-NA-L
2	FAZ-B2/1-NA-L	FAZ-B2/2-NA-L	FAZ-B2/3-NA-L
3	FAZ-B3/1-NA-L	FAZ-B3/2-NA-L	FAZ-B3/3-NA-L
4	FAZ-B4/1-NA-L	FAZ-B4/2-NA-L	FAZ-B4/3-NA-L
5	FAZ-B5/1-NA-L	FAZ-B5/2-NA-L	FAZ-B5/3-NA-L
6	FAZ-B6/1-NA-L	FAZ-B6/2-NA-L	FAZ-B6/3-NA-L
7	FAZ-B7/1-NA-L	FAZ-B7/2-NA-L	FAZ-B7/3-NA-L
8	FAZ-B8/1-NA-L	FAZ-B8/2-NA-L	FAZ-B8/3-NA-L
10	FAZ-B10/1-NA-L	FAZ-B10/2-NA-L	FAZ-B10/3-NA-L
13	FAZ-B13/1-NA-L	FAZ-B13/2-NA-L	FAZ-B13/3-NA-L
15	FAZ-B15/1-NA-L	FAZ-B15/2-NA-L	FAZ-B15/3-NA-L
16	FAZ-B16/1-NA-L	FAZ-B16/2-NA-L	FAZ-B16/3-NA-L
20	FAZ-B20/1-NA-L	FAZ-B20/2-NA-L	FAZ-B20/3-NA-L
25	FAZ-B25/1-NA-L	FAZ-B25/2-NA-L	FAZ-B25/3-NA-L
30	FAZ-B30/1-NA-L	FAZ-B30/2-NA-L	FAZ-B30/3-NA-L
32	FAZ-B32/1-NA-L	FAZ-B32/2-NA-L	FAZ-B32/3-NA-L
35 ②	FAZ-B35/1-NA	FAZ-B35/2-NA	FAZ-B35/3-NA
40 ②	FAZ-B40/1-NA	FAZ-B40/2-NA	FAZ-B40/3-NA

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC B Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
B Curve with Ring-Tongue Terminals (3–5X I_n Current Rating)			
1	FAZ-B1/1-RT-L	FAZ-B1/2-RT-L	FAZ-B1/3-RT-L
1.5	FAZ-B1.5/1-RT-L	FAZ-B1.5/2-RT-L	FAZ-B1.5/3-RT-L
2	FAZ-B2/1-RT-L	FAZ-B2/2-RT-L	FAZ-B2/3-RT-L
3	FAZ-B3/1-RT-L	FAZ-B3/2-RT-L	FAZ-B3/3-RT-L
4	FAZ-B4/1-RT-L	FAZ-B4/2-RT-L	FAZ-B4/3-RT-L
5	FAZ-B5/1-RT-L	FAZ-B5/2-RT-L	FAZ-B5/3-RT-L
6	FAZ-B6/1-RT-L	FAZ-B6/2-RT-L	FAZ-B6/3-RT-L
7	FAZ-B7/1-RT-L	FAZ-B7/2-RT-L	FAZ-B7/3-RT-L
8	FAZ-B8/1-RT-L	FAZ-B8/2-RT-L	FAZ-B8/3-RT-L
10	FAZ-B10/1-RT-L	FAZ-B10/2-RT-L	FAZ-B10/3-RT-L
13	FAZ-B13/1-RT-L	FAZ-B13/2-RT-L	FAZ-B13/3-RT-L
15	FAZ-B15/1-RT-L	FAZ-B15/2-RT-L	FAZ-B15/3-RT-L
16	FAZ-B16/1-RT-L	FAZ-B16/2-RT-L	FAZ-B16/3-RT-L
20	FAZ-B20/1-RT-L	FAZ-B20/2-RT-L	FAZ-B20/3-RT-L
25	FAZ-B25/1-RT-L	FAZ-B25/2-RT-L	FAZ-B25/3-RT-L
30	FAZ-B30/1-RT-L	FAZ-B30/2-RT-L	FAZ-B30/3-RT-L
32	FAZ-B32/1-RT-L	FAZ-B32/2-RT-L	FAZ-B32/3-RT-L
35 ②	FAZ-B35/1-RT	FAZ-B35/2-RT	FAZ-B35/3-RT
40 ②	FAZ-B40/1-RT	FAZ-B40/2-RT	FAZ-B40/3-RT

Notes

① Two-piece order. Quantities of two per box.

② 35A and 40A at 240 Vac were available prior to the creation of the FAZ-NA-L offering so the catalog numbers at these amperages exclude the "L" suffix.

1

FAZ-NA UL 489 Circuit Breakers at 240 Vac—10 kAIC C Curve

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC C Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
C Curve (5–10X I_n Current Rating)			
0.5	FAZ-C0.5/1-NA-L	FAZ-C0.5/2-NA-L	FAZ-C0.5/3-NA-L
1	FAZ-C1/1-NA-L	FAZ-C1/2-NA-L	FAZ-C1/3-NA-L
1.5	FAZ-C1.5/1-NA-L	FAZ-C1.5/2-NA-L	FAZ-C1.5/3-NA-L
2	FAZ-C2/1-NA-L	FAZ-C2/2-NA-L	FAZ-C2/3-NA-L
3	FAZ-C3/1-NA-L	FAZ-C3/2-NA-L	FAZ-C3/3-NA-L
4	FAZ-C4/1-NA-L	FAZ-C4/2-NA-L	FAZ-C4/3-NA-L
5	FAZ-C5/1-NA-L	FAZ-C5/2-NA-L	FAZ-C5/3-NA-L
6	FAZ-C6/1-NA-L	FAZ-C6/2-NA-L	FAZ-C6/3-NA-L
7	FAZ-C7/1-NA-L	FAZ-C7/2-NA-L	FAZ-C7/3-NA-L
8	FAZ-C8/1-NA-L	FAZ-C8/2-NA-L	FAZ-C8/3-NA-L
10	FAZ-C10/1-NA-L	FAZ-C10/2-NA-L	FAZ-C10/3-NA-L
13	FAZ-C13/1-NA-L	FAZ-C13/2-NA-L	FAZ-C13/3-NA-L
15	FAZ-C15/1-NA-L	FAZ-C15/2-NA-L	FAZ-C15/3-NA-L
16	FAZ-C16/1-NA-L	FAZ-C16/2-NA-L	FAZ-C16/3-NA-L
20	FAZ-C20/1-NA-L	FAZ-C20/2-NA-L	FAZ-C20/3-NA-L
25	FAZ-C25/1-NA-L	FAZ-C25/2-NA-L	FAZ-C25/3-NA-L
30	FAZ-C30/1-NA-L	FAZ-C30/2-NA-L	FAZ-C30/3-NA-L
32	FAZ-C32/1-NA-L	FAZ-C32/2-NA-L	FAZ-C32/3-NA-L
35 ②	FAZ-C35/1-NA-SP	FAZ-C35/2-NA	FAZ-C35/3-NA
40 ②	FAZ-C40/1-NA-SP	FAZ-C40/2-NA	FAZ-C40/3-NA

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC C Curve (15–25A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
C Curve with Ring-Tongue Terminals (5–10X I_n Current Rating)			
0.5	FAZ-C0.5/1-RT-L	FAZ-C0.5/2-RT-L	FAZ-C0.5/3-RT-L
1	FAZ-C1/1-RT-L	FAZ-C1/2-RT-L	FAZ-C1/3-RT-L
1.5	FAZ-C1.5/1-RT-L	FAZ-C1.5/2-RT-L	FAZ-C1.5/3-RT-L
2	FAZ-C2/1-RT-L	FAZ-C2/2-RT-L	FAZ-C2/3-RT-L
3	FAZ-C3/1-RT-L	FAZ-C3/2-RT-L	FAZ-C3/3-RT-L
4	FAZ-C4/1-RT-L	FAZ-C4/2-RT-L	FAZ-C4/3-RT-L
5	FAZ-C5/1-RT-L	FAZ-C5/2-RT-L	FAZ-C5/3-RT-L
6	FAZ-C6/1-RT-L	FAZ-C6/2-RT-L	FAZ-C6/3-RT-L
7	FAZ-C7/1-RT-L	FAZ-C7/2-RT-L	FAZ-C7/3-RT-L
8	FAZ-C8/1-RT-L	FAZ-C8/2-RT-L	FAZ-C8/3-RT-L
10	FAZ-C10/1-RT-L	FAZ-C10/2-RT-L	FAZ-C10/3-RT-L
13	FAZ-C13/1-RT-L	FAZ-C13/2-RT-L	FAZ-C13/3-RT-L
15	FAZ-C15/1-RT-L	FAZ-C15/2-RT-L	FAZ-C15/3-RT-L
16	FAZ-C16/1-RT-L	FAZ-C16/2-RT-L	FAZ-C16/3-RT-L
20	FAZ-C20/1-RT-L	FAZ-C20/2-RT-L	FAZ-C20/3-RT-L
25	FAZ-C25/1-RT-L	FAZ-C25/2-RT-L	FAZ-C25/3-RT-L
30	FAZ-C30/1-RT-L	FAZ-C30/2-RT-L	FAZ-C30/3-RT-L
32	FAZ-C32/1-RT-L	FAZ-C32/2-RT-L	FAZ-C32/3-RT-L
35 ②	FAZ-C35/1-RT-SP	FAZ-C35/2-RT	FAZ-C35/3-RT
40 ②	FAZ-C40/1-RT-SP	FAZ-C40/2-RT	FAZ-C40/3-RT

Notes

① Two-piece order. Quantities of two per box.

② 35A and 40A at 240 Vac were available prior to the creation of the FAZ-NA-L offering so the catalog numbers at these amperages exclude the "L" suffix.

FAZ-NA UL 489 Circuit Breakers at 240 Vac—10 kAIC D Curve

- UL approved (UL 489) and CSA Certified (CSA C22.2 No.5-02) as branch circuit breakers
- Interrupting capacity: 10 kA UL/CSA; 15 kA IEC 60947-2
- Current limiting device
- UL file number E235139



Single-Pole

Two-Pole

Three-Pole

FAZ-NA UL 489 Circuit Breakers at 277/480 Vac—10 kAIC, 14 kAIC D Curve (13–20A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
D Curve (10–20X I_n Current Rating)			
0.5	FAZ-D0.5/1-NA-L	FAZ-D0.5/2-NA-L	FAZ-D0.5/3-NA-L
1	FAZ-D1/1-NA-L	FAZ-D1/2-NA-L	FAZ-D1/3-NA-L
1.5	FAZ-D1.5/1-NA-L	FAZ-D1.5/2-NA-L	FAZ-D1.5/3-NA-L
2	FAZ-D2/1-NA-L	FAZ-D2/2-NA-L	FAZ-D2/3-NA-L
3	FAZ-D3/1-NA-L	FAZ-D3/2-NA-L	FAZ-D3/3-NA-L
4	FAZ-D4/1-NA-L	FAZ-D4/2-NA-L	FAZ-D4/3-NA-L
5	FAZ-D5/1-NA-L	FAZ-D5/2-NA-L	FAZ-D5/3-NA-L
6	FAZ-D6/1-NA-L	FAZ-D6/2-NA-L	FAZ-D6/3-NA-L
7	FAZ-D7/1-NA-L	FAZ-D7/2-NA-L	FAZ-D7/3-NA-L
8	FAZ-D8/1-NA-L	FAZ-D8/2-NA-L	FAZ-D8/3-NA-L
10	FAZ-D10/1-NA-L	FAZ-D10/2-NA-L	FAZ-D10/3-NA-L
13	FAZ-D13/1-NA-L	FAZ-D13/2-NA-L	FAZ-D13/3-NA-L
15	FAZ-D15/1-NA-L	FAZ-D15/2-NA-L	FAZ-D15/3-NA-L
16	FAZ-D16/1-NA-L	FAZ-D16/2-NA-L	FAZ-D16/3-NA-L
20	FAZ-D20/1-NA-L	FAZ-D20/2-NA-L	FAZ-D20/3-NA-L
25	FAZ-D25/1-NA-L	FAZ-D25/2-NA-L	FAZ-D25/3-NA-L
30	FAZ-D30/1-NA-L	FAZ-D30/2-NA-L	FAZ-D30/3-NA-L
32	FAZ-D32/1-NA-L	FAZ-D32/2-NA-L	FAZ-D32/3-NA-L
35 ②	FAZ-D35/1-NA-SP	FAZ-D35/2-NA	FAZ-D35/3-NA
40 ②	FAZ-D40/1-NA-SP	FAZ-D40/2-NA	FAZ-D40/3-NA

Single-Pole

Two-Pole

Three-Pole

FAZ-RT UL 489 Circuit Breakers with Ring-Tongue Terminals at 277/480 Vac—10 kAIC, 14 kAIC D Curve (13–20A)

Amps	Single-Pole ① Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
D Curve with Ring-Tongue Terminals (10–20X I_n Current Rating)			
0.5	FAZ-D0.5/1-RT-L	FAZ-D0.5/2-RT-L	FAZ-D0.5/3-RT-L
1	FAZ-D1/1-RT-L	FAZ-D1/2-RT-L	FAZ-D1/3-RT-L
1.5	FAZ-D1.5/1-RT-L	FAZ-D1.5/2-RT-L	FAZ-D1.5/3-RT-L
2	FAZ-D2/1-RT-L	FAZ-D2/2-RT-L	FAZ-D2/3-RT-L
3	FAZ-D3/1-RT-L	FAZ-D3/2-RT-L	FAZ-D3/3-RT-L
4	FAZ-D4/1-RT-L	FAZ-D4/2-RT-L	FAZ-D4/3-RT-L
5	FAZ-D5/1-RT-L	FAZ-D5/2-RT-L	FAZ-D5/3-RT-L
6	FAZ-D6/1-RT-L	FAZ-D6/2-RT-L	FAZ-D6/3-RT-L
7	FAZ-D7/1-RT-L	FAZ-D7/2-RT-L	FAZ-D7/3-RT-L
8	FAZ-D8/1-RT-L	FAZ-D8/2-RT-L	FAZ-D8/3-RT-L
10	FAZ-D10/1-RT-L	FAZ-D10/2-RT-L	FAZ-D10/3-RT-L
13	FAZ-D13/1-RT-L	FAZ-D13/2-RT-L	FAZ-D13/3-RT-L
15	FAZ-D15/1-RT-L	FAZ-D15/2-RT-L	FAZ-D15/3-RT-L
16	FAZ-D16/1-RT-L	FAZ-D16/2-RT-L	FAZ-D16/3-RT-L
20	FAZ-D20/1-RT-L	FAZ-D20/2-RT-L	FAZ-D20/3-RT-L
25	FAZ-D25/1-RT-L	FAZ-D25/2-RT-L	FAZ-D25/3-RT-L
30	FAZ-D30/1-RT-L	FAZ-D30/2-RT-L	FAZ-D30/3-RT-L
32	FAZ-D32/1-RT-L	FAZ-D32/2-RT-L	FAZ-D32/3-RT-L
35 ②	FAZ-D35/1-RT-SP	FAZ-D35/2-RT	FAZ-D35/3-RT
40 ②	FAZ-D40/1-RT-SP	FAZ-D40/2-RT	FAZ-D40/3-RT

Notes

① Two-piece order. Quantities of two per box.

② 35A and 40A at 240 Vac were available prior to the creation of the FAZ-NA-L offering so the catalog numbers at these amperages exclude the "L" suffix.

1

Accessories

FAZ-NA and FAZ-NA-L UL 489 Breakers

	Description	Catalog Number
Contact	Two-pole contact or auxiliary contact/trip indicating contact	**Z-NHK** ①
Auxiliary Contact	Auxiliary contact	**Z-IHK-NA**
Shunt Trip	Shunt trip 110–415 Vac	**FAZ-XAA-NA110-415VAC**
	Shunt trip 12–110 Vac	**FAZ-XAA-NA12-110VAC**
Padlock Hasp 	Padlock hasp	**Z-IS/SPE-1TE**
Lockoff Device 	UL lockoff device	**FAZPLOFF**

FAZ-NA and FAZ-NA-L UL 489 Breakers, continued

	Description	Catalog Number
Busbar	Busbar—single-pole, 6 terminals ②③④⑤	**Z-SV/UL-16/1P-1TE/6**
	Busbar—single-pole, 12 terminals ②③④⑤	**Z-SV/UL-16/1P-1TE/12**
	Busbar—single-pole, 18 terminals ②③④⑤	**Z-SV/UL-16/1P-1TE/18**
	Busbar—two-pole, 6 terminals ②③④⑤	**Z-SV/UL-16/2P-2TE/6**
	Busbar—two-pole, 12 terminals ②③④⑤	**Z-SV/UL-16/2P-2TE/12**
	Busbar—two-pole, 18 terminals ②③④⑤	**Z-SV/UL-16/2P-2TE/18**
	Busbar—three-pole, 6 terminals ②③④⑤	**Z-SV/UL-16/3P-3TE/6**
	Busbar—three-pole, 12 terminals ②③④⑤	**Z-SV/UL-16/3P-3TE/12**
	Busbar—three-pole, 18 terminals ②③④⑤	**Z-SV/UL-16/3P-3TE/18**
Busbar Shroud	Three-pole busbar shroud	**ZV-BS-UL**
Extension Terminal 	Extension terminal—35 mm² (10–1/0 AWG)	**Z-EK/35/UL**
Bus Connector 	Bus connector—conductors up to 50 mm² (~1/0 AWG)	**Z-EB/50/UL**

Notes

① Voltage of FAZ-NA circuit breaker is limited to 300V with this auxiliary contact installed.
② Do not cut commoning link.
③ A maximum of three commoning links may be used in conjunction. Each breaker connected to the commoning link must have the same number of poles for proper use.
④ Not for use with ring-tongue circuit breakers.
⑤ Bus may be center fed for high current capacity.

Tripping Signal Switch Z-NHK, Z-IHK-NA

- Design according to IEC/EN 60947-5-1, IEC/EN 62019
- Field installable
- The specified minimum voltages are per contact—take into account particularly in case of series connection
- Self-cleaning contacts
- Contact material and design particularly suitable for extra low voltage
- Z-NHK: the function of one of the two change-over contacts can be switched from "auxiliary switch" to "tripping signal switch"
- Tripping signal contact transmits message of electric tripping, not mechanical switch-off
- Test key for contact function "electrical tripping"
- Z-IHK-NA: will allow for > 480Y/277 Vac rating

Connection Diagram



Busbar Connection Example



Z-NHK

Z-IHK-NA

Contact and Auxiliary Contact

Description	Z-NHK	Z-IHK-NA
Electrical		
Contact function	2CO	1NO + 1NC
Rated voltage	230V	250V
Frequency	50/60 Hz	50/60 Hz
Rated current	2A	6A
Rated thermal current I_{th}	2A	6A
Utilization category AC13 Rated operational current I_e	3A/250 Vac	3A/250 Vac
Utilization category AC15 Rated operational current I_e	2A/250 Vac	2A/250 Vac
Utilization category DC12 Rated operational current I_e	0.5A/110 Vdc	0.5A/110 Vdc 0.25A/220 Vdc
Rated insulation voltage U_i	250 Vac	250 Vac
Minimum operational voltage per contact U_{min}	5 Vdc	5 Vdc
Minimum operational current I_{min}	10 mA DC	10 mA AC/DC
Rated peak withstand voltage U_{imp} (1.2/50µ)	2.5 kV	4 kV
Conditional short-circuit current I_k with backup fuse 6A	1 kA	1 kA
Max. backup fuse, overload and short circuit	6A gL	—
Mechanical		
Tripping indicator "electrical tripping"	Blue/white	—
Frame size	45 mm	45 mm
Device height	80 mm	80 mm
Device width	8.8 mm (0.5MU)	8.8 mm (0.5MU)
Mounting	Onto switching device	—
Degree of protection, built-in	IP40	IP40
Terminal protection	Finger and hand touch safe According to BGV A3, ÖVE-EN 6	Finger and hand touch safe According to BGV A3, ÖVE-EN 6
Terminals	Lift terminals	Lift terminals
Terminal capacity	20–14 AWG	0.5–2.5 mm^2
Terminal screws	M3 (Posidrive Z0)	M3 (Posidrive Z0)
Fastening torque of terminal screws	7 lb-in	Max. 1.2 Nm



Shunt trip release FAZ-XAA-NA

- Remote release for subsequent mounting onto FAZ-NA/RT
- Additional installation of standard auxiliary switch is possible
- Position indicator red–green

Connection Diagram



Shunt Trip Release FAZ-XAA-NA

Description	FAZ-XAA-NA12-110VAC	FAZ-XAA-NA110-415VAC
Electrical		
Can be mounted onto	FAZ-NA / FAZ-NA-DC / FAZ-RT	FAZ-NA / FAZ-NA-DC / FAZ-RT
Operational voltage range	12–110 Vac 12–60 Vdc	110–415 Vac 110–230 Vdc
Frequency	50/60 Hz	50/60 Hz
Mechanical		
Frame size	45 mm	45 mm
Device height	105 mm	105 mm
Device width	17.5 mm	17.5 mm
Mounting	Quick fastening with two lock-in positions on EN 50022	
Degree of protection, built-in	IP40	IP40
Terminal protection	Finger and hand touch safe according to BGV A3, ÖVE-EN 6	
Terminals	Open mouthed/lift	Open mouthed/lift
Terminal capacity One and two wires	18–10 AWG	18–10 AWG

Busbar block UL 489 (pin)

- Tested according to UL 489
- Do not cut
- Extension terminal 35 mm^2 Z-EK/35/UL for copper conductors
- Incoming terminal 50 mm^2 Z-EB/50/UL
- For covering of not used pins, use busbar tag shrouds ZV-BS-UL

Connection Diagrams

Three-Pole Busbar



Two-Pole Busbar



Single-Pole Busbar



Busbar Block UL 489 (Pin)

Description	UL 489	IEC/EN 60947-2
Electrical		
Rated operational voltage	480/277 Vac 96 Vdc	—
Rated frequency	50/60 Hz	—
Rated voltage	480 Vac	690 Vac
Overvoltage category	—	III
Rated impulse withstand voltage U_{imp}	—	9.5 kV
Rated current	80A at 40°C	80A at 30°C
Rated conditional short-circuit current AC with 350A gG	—	15 kA
Short-circuit current	10 kA	—
Mechanical		
Busbar cross section	—	16 mm^2 Cu
Flame class according to UL 94	V0	—
Pollution degree	—	2
Comparative tracking index	—	CTI 600
Minimum clearance (internal/external)	—	> 9.5/25.4 mm
Minimum creepage distance (internal/external)	—	> 12.7/50.8 mm
Resistance to climatic conditions	—	According to DIN/EN 60068

1

Technical Data and Specifications

Trip Curve Chart

Eaton FAZ-NA and FAZ-NA-L branch circuit breakers are available with "B," "C" and "D" tripping characteristics. B-curve devices are suitable for applications where low levels of inrush current are expected.

C-curve devices are suitable for applications where medium levels of inrush current are expected. Applications include small transformers, lighting, pilot devices, control circuits and coils. C-curve devices provide a medium magnetic trip point.

D-curve devices are suitable for applications where high levels of inrush current are expected. The high magnetic trip point prevents nuisance tripping in high inductive applications such as motors, transformers and power supplies.

Eaton FAZ-NA and FAZ-NA-L devices are current limiting, which means they interrupt fault currents within one half cycle of the fault. Current limiting devices offer superior protection by reducing peak let-through current and energy.

Tripping Characteristics



Connection Diagrams

Single-Pole

Two-Pole



Three-Pole



UL 489 Miniature Circuit Breakers Technical Data

Description	FAZ-NA	FAZ-NA-DC	FAZ-NA-L
Electrical			
Design according to	UL 489, CSA C22.2 No.5, IEC 60947-2	UL 489, CSA C22.2 No.5, IEC 60947-2	UL 489, CSA C22.2 No.5, IEC 60947-2
Rated voltage	Single-pole: 277 Vac 2- or 3-pole: 277/480 Vac	125 Vdc per pole 250 Vdc with 2-poles in connected series	Single-pole: 240 Vac 2- or 3-pole: 240 Vac
	Single-pole: 48 Vdc per pole 2-pole in series: 96 Vdc	—	Single-pole: 48 Vdc per pole 2-pole in series: 96 Vdc
Rated current	B: 1–32 A C & D: 0.5–32 A	C: 2–40 A	B: 1–40 A C & D: 0.5–40 A
Characteristic	B, C, D	C	B, C, D
Current interrupting rating	B curve—10 kA: 1–13 A, 30–32 A C curve—10 kA: 0.5–13 A, 30–32 A B & C curve—14 kA: 15–25 A D curve—10 kA: 0.5–10 A, 25–32 A D curve—14 kA: 13–20 A	10 kA	B curve—10 kA: 1–13 A, 30–32 A C curve—10 kA: 0.5–13 A, 30–32 A B & C curve—14 kA: 15–25 A D curve—10 kA: 0.5–10 A, 25–32 A D curve—14 kA: 13–20 A
Rated frequency	50/60 Hz	50/60 Hz	50/60 Hz
Endurance	≥ 20,000 operations	≥ 20,000 operations	≥ 20,000 operations
Line voltage connection	Suitable for reverse feed	Suitable for reverse feed	Suitable for reverse feed
Mechanical			
Frame size	45 mm	45 mm	45 mm
Device height	105 mm	105 mm	105 mm
Device width	17.7 mm per pole	17.7 mm per pole	17.7 mm per pole
Terminal protection	Finger and hand touch safe according to BGV A3, OVE-EN 6	Finger and hand touch safe according to BGV A3, OVE-EN 6	Finger and hand touch safe according to BGV A3, OVE-EN 6
Mounting	Quick fastening with two lock-in positions on IEC/EN 60715	Quick fastening with two lock-in positions on IEC/EN 60715	Quick fastening with two lock-in positions on IEC/EN 60715
Upper and lower terminals	Open mouth/lift terminals	Open mouth/lift terminals	Open mouth/lift terminals
Terminal capacity	One wire: AWG 18–6 Two wires: AWG 18–10	One wire: AWG 18–6 Two wires: AWG 18–10	One wire: AWG 18–6 Two wires: AWG 18–10
Terminal fastening torque	AWG 18–21: 21 lb-in AWG 10–8: 25 lb-in AWG 6: 36 lb-in	AWG 18–21: 21 lb-in AWG 10–8: 25 lb-in AWG 6: 36 lb-in	AWG 18–21: 21 lb-in AWG 10–8: 25 lb-in AWG 6: 36 lb-in
Mounting	Independent of position	Independent of position	Independent of position
Calibration temperature UL 489, CSA C22.2 No.5	40°C	40°C	40°C
IEC 60947-2	30°C	30°C	30°C

Power Loss at I_n

	Characteristic B			Characteristic C			Characteristic D		
I_n [A]	Single-Pole P [W]	Two-Pole P [W]	Three-Pole P [W]	Single-Pole P [W]	Two-Pole P [W]	Three-Pole P [W]	Single-Pole P [W]	Two-Pole P [W]	Three-Pole P [W]
0.5	—	—	—	1.6	3.2	4.7	1.6	3.2	4.8
1.0	1.1	2.2	3.4	1.1	2.2	3.4	0.8	1.5	2.3
1.5	2.2	4.4	6.6	1.3	2.6	3.9	1.0	2.1	3.1
2.0	1.4	2.8	4.3	1.4	2.8	4.3	1.0	2.1	3.1
3.0	2.1	4.2	6.4	1.2	2.4	3.6	1.2	2.4	3.6
4.0	1.4	2.9	4.3	1.4	2.9	4.3	1.4	2.9	4.3
5.0	1.8	3.7	5.5	1.9	3.7	5.6	1.5	2.9	4.4
6.0	1.7	3.5	5.2	1.2	2.3	3.5	1.2	2.3	3.5
7.0	2.0	4.0	6.0	1.4	2.8	4.3	1.4	2.8	4.3
8.0	2.0	3.9	5.9	1.4	2.8	4.2	1.2	2.4	3.7
10.0	1.8	3.6	5.3	1.8	3.6	5.3	1.5	3.0	4.5
13.0	2.4	4.7	7.1	2.4	4.7	7.1	2.0	4.1	6.1
15.0	1.9	3.8	5.6	1.9	3.8	5.6	1.5	3.1	4.6
16.0	2.1	4.3	6.4	2.1	4.3	6.4	1.7	3.5	5.2
20.0	2.9	5.8	8.7	2.9	5.8	8.7	1.8	3.7	5.5
25.0	3.1	6.2	9.3	3.1	6.2	9.3	2.6	5.1	7.7
30.0	3.0	6.0	9.0	3.0	6.0	9.0	2.7	5.4	8.1
32.0	3.4	6.8	10.2	3.4	6.8	10.2	3.1	6.2	9.3
35.0	4.0	8.1	12.1	3.7	7.4	11.0	3.8	7.6	11.3
40.0	4.0	8.1	12.1	4.0	8.1	12.1	3.9	7.8	11.6

Let-Through Energy

Characteristic B (1–32A), 277V



Characteristic B (35–40A), 240V



Characteristic C (0.5–32A), 277V



Characteristic C (40A), 240V



Characteristic D (0.5–32A), 277V



Characteristic D (40A), 240V



Influence of Ambient Temperature T on Load Carrying Capacity

Device Market Current Rating I_n (A) at 40°C	I_n (A) at Higher Ambient Temperature							
	15°C	20°C	25°C	30°C	40°C	50°C	55°C	60°C
0.5	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5
1.0	1.1	1.1	1.1	1.0	1.0	1.0	0.9	0.9
1.5	1.7	1.6	1.6	1.6	1.5	1.4	1.4	1.4
2.0	2.2	2.2	2.1	2.1	2.0	1.9	1.9	1.8
3.0	3.3	3.2	3.2	3.1	3.0	2.9	2.9	2.8
4.0	4.4	4.3	4.2	4.2	4.0	3.8	3.8	3.7
5.0	5.5	5.4	5.3	5.2	5.0	4.8	4.7	4.6
6.0	6.6	6.5	6.4	6.2	6.0	5.8	5.6	5.5
7.0	7.7	7.6	7.4	7.3	7.0	6.7	6.6	6.4
8.0	8.8	8.6	8.5	8.3	8.0	7.7	7.5	7.4
10.0	11.0	10.8	10.6	10.4	10.0	9.6	9.4	9.2
13.0	14.3	14.0	13.8	13.5	13.0	12.5	12.5	12.0
15.0	16.5	16.2	15.9	15.6	15.0	14.4	14.1	13.8
16.0	17.6	17.3	17.0	16.6	16.0	15.4	15.0	14.7
20.0	22.0	21.6	21.2	20.8	20.0	19.2	18.8	18.4
25.0	27.5	27.0	26.5	26.0	25.0	24.0	23.3	23.0
30.0	33.0	32.4	31.8	31.2	30.0	28.8	28.2	27.6
32.0	35.2	34.6	33.9	33.3	32.0	30.7	30.1	29.4
40.0	44.0	43.2	42.4	41.6	40.0	38.4	37.6	36.8



Maximum Load I_L at ambient temperature T: I_L (T) = I_N K_T(T)

Load Carrying Capacity of Adjoining Miniature Circuit Breakers



1

Dimensions

Approximate Dimensions in Inches (mm)

Miniature Circuit Breakers



Lockout Attachment—Z-IS/SPE-1TE



UL Lockoff Device—FAZPLOFF



Accessories

Z-SV/UL-16/6



Z-SV/UL-18...12



ZV-BS-UL



Z-SV/UL-16.../18



Z-EK/35/UL



Z-EK/35/UL

Description	UL 489	IEC/EN 60947-2
U_e	480 Vac/96 Vdc	240/415 Vac
f	50/60 Hz	50/60 Hz
U_{imp}	—	9.5 kV
I_e	80A at 40°C	80A at 30°C
	10–1/0 AWG 60/75°C Cu	2.5–35 mm² Cu
	0.56 in	14 mm

Z-EB/50/UL

Description	UL 489	IEC/EN 60947-2
U_e	480 Vac/96 Vdc	240/415 Vac
f	50/60 Hz	50/60 Hz
U_{imp}	—	9.5 kV
I_e	115A at 40°C	160A at 30°C
	#1–14 AWG 60/75°C Cu	1.5–50 mm² Cu
	0.56 in	14 mm

Application Guidelines

Example of UL 489 and UL 1077 Application



Example of UL 489 and UL 1077 Application

UL 489 circuit breakers

Used for branch circuit protection, internal/external receptacles, external motors and HACR equipment (heating, air conditioning and refrigeration).

UL 1077 supplementary protectors

Used for overcurrent protection within appliances or electrical equipment, where branch circuit protection is already provided or not required.

Note: UL 489 devices can be used in place of UL 1077; UL 1077 devices cannot be used in place of UL 489.

FAZ Circuit Breakers

Optimum and Efficient Protection for Every Application

Contents

Description	*Page*
FAZ Circuit Breakers	**V4-T1-70**
Catalog Number Selection	**V4-T1-71**
Standards and Certifications	**V4-T1-71**
Product Selection	**V4-T1-72**
Accessories	**V4-T1-78**
Technical Data and Specifications	**V4-T1-81**
Dimensions	**V4-T1-88**

FAZ Circuit Breakers

Product Overview

Optimum product quality, tested reliability and safety stand for best protection of personnel, installations and plant. Eaton's FAZ DIN rail mountable circuit breaker is designed for use in control panel applications.

Powerful offering for machine and system builders

The FAZ is available with B, C, D, K, S, and Z characteristics in accordance with UL 1077, CSA C22.2 No.235 and IEC 60947-2. These devices are CE marked.

Application Description

- Supplementary protection
- Control circuits
- Lighting
- Business equipment
- Appliances

Features

- Complete range of UL 1077 recognized DIN rail mounted miniature circuit breakers up to 63A current rating
- Standard ratings of 10 kAIC up to 277/480 Vac
- Current limiting design provides fast short-circuit interruption that reduces the let-through energy, which can damage the circuit
- Suitable for supplementary protection
- Thermal-magnetic overcurrent protection
  - Six levels of short-circuit protection, categorized by B, C, D, K, S, and Z curves
- Trip-free design—breaker can not be defeated by holding the handle in the ON position
- Captive screws cannot be lost
- Fulfill UL 1077, CSA C22.2 No.235 and also IEC 60947-2 Standard
- Field-installable shunt trip and auxiliary switch subsequent mounting
- Module width of only 17.7 mm (per pole)
- Contact position indicator (red/green)
- Easy installation on DIN rail
- Possibility for sealing the toggle in ON or OFF position

Discover These Advanced Features

Breakers install on standard DIN rail

Available in one-, two-, three-, four-pole, 1+N and 3+N models

Color-coded indicator provides breaker status for easy troubleshooting

Captive Posidrive terminal screws with finger and back-of-hand protection (IP20)

Trip-free design; breaker cannot be defeated by holding the handle in the ON position

Breaker information printed on the front of the device for quick identification

Standards and Certifications

FAZ complies with the latest national and international standards.

- UL 1077, CSA C22.2 No. 235
  - Apply to supplementary protectors intended for use as overcurrent, or overvoltage or undervoltage protection within an appliance or other electrical equipment where branch circuit protection is already provided, or is not required
- RoHS compliant
- VDE compliant
  - Devices with B, C, and D curves are VDE compliant
- CCC
  - Devices with B, C, and D curves are CCC compliant
- ABS compliant

Catalog Number Selection

FAZ C 6 / 1 SP

Breaker Family	Trip Characteristics ①	Ampere Rating	Number of Poles	Single Package
FAZ = Supplementary protector	**B** = 3–5X I_n **C** = 5–10X I_n **D** = 10–20X I_n **K** = 8–12X I_n **S** = 13–17X I_n **Z** = 2–3X I_n	**0.5** = 0.5A **1** = 1A **2** = 2A **3** = 3A **4** = 4A **5** = 5A **6** = 6A **7** = 7A **8** = 8A **10** = 10A **13** = 13A **15** = 15A **16** = 16A **20** = 20A **25** = 25A **30** = 30A **32** = 32A **40** = 40A **50** = 50A **63** = 63A	**1** = Single-pole **2** = Two-pole **3** = Three-pole **4** = Single-pole **1N** = Single-pole + neutral **3N** = Three-pole + neutral	**SP** = Single packaging of single-pole curve B, C and D for select amperes only **Blank** = Standard packaging

Note

① I_n = Rated current for instantaneous trip characteristics.

1

Product Selection

FAZ B curve (3–5X I_n current rating)

- Designed for resistive or slightly inductive loads
- Response time of instantaneous trip: 3–5X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)
- UL file number 177451

Suitable for applications where protection against low-level short-circuit faults in control wiring is desired. Instantaneous trip is 3–5X continuous rating of device (I_n). Applications include PLC wiring, business equipment, lighting, appliances and some motors. Low magnetic trip point.



Single-Pole

Two-Pole

Three-Pole

B Curve (3–5X I_n Current Rating)—Designed for Resistive or Slightly Inductive Loads ①

Amperes	Single-Pole ② Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
1	FAZ-B1/1-SP	FAZ-B1/2	FAZ-B1/3
2	FAZ-B2/1-SP	FAZ-B2/2	FAZ-B2/3
3	FAZ-B3/1-SP	FAZ-B3/2	FAZ-B3/3
4	FAZ-B4/1-SP	FAZ-B4/2	FAZ-B4/3
5	FAZ-B5/1-SP	FAZ-B5/2	FAZ-B5/3
6	FAZ-B6/1-SP	FAZ-B6/2	FAZ-B6/3
7	FAZ-B7/1-SP	FAZ-B7/2	FAZ-B7/3
8	FAZ-B8/1-SP	FAZ-B8/2	FAZ-B8/3
10	FAZ-B10/1-SP	FAZ-B10/2	FAZ-B10/3
12	FAZ-B12/1-SP	FAZ-B12/2	FAZ-B12/3
13	FAZ-B13/1-SP	FAZ-B13/2	FAZ-B13/3
15	FAZ-B15/1-SP	FAZ-B15/2	FAZ-B15/3
16	FAZ-B16/1-SP	FAZ-B16/2	FAZ-B16/3
20	FAZ-B20/1-SP	FAZ-B20/2	FAZ-B20/3
25	FAZ-B25/1-SP	FAZ-B25/2	FAZ-B25/3
30	FAZ-B30/1-SP	FAZ-B30/2	FAZ-B30/3
32	FAZ-B32/1-SP	FAZ-B32/2	FAZ-B32/3
40	FAZ-B40/1-SP	FAZ-B40/2	FAZ-B40/3
50	FAZ-B50/1-SP	FAZ-B50/2	FAZ-B50/3
63	FAZ-B63/1-SP	FAZ-B63/2	FAZ-B63/3

Four-Pole

Single-Pole + Neutral

Three-Pole + Neutral

B Curve (3–5X I_n Current Rating)—Designed for Resistive or Slightly Inductive Loads, continued ①

Amperes	Four-Pole Catalog Number	Single-Pole + Neutral Catalog Number	Three-Pole + Neutral Catalog Number
1	FAZ-B1/4	FAZ-B1/1N	FAZ-B1/3N
2	FAZ-B2/4	FAZ-B2/1N	FAZ-B2/3N
3	FAZ-B3/4	FAZ-B3/1N	FAZ-B3/3N
4	FAZ-B4/4	FAZ-B4/1N	FAZ-B4/3N
5	FAZ-B5/4	FAZ-B5/1N	FAZ-B5/3N
6	FAZ-B6/4	FAZ-B6/1N	FAZ-B6/3N
7	FAZ-B7/4	FAZ-B7/1N	FAZ-B7/3N
8	FAZ-B8/4	FAZ-B8/1N	FAZ-B8/3N
10	FAZ-B10/4	FAZ-B10/1N	FAZ-B10/3N
12	FAZ-B12/4	FAZ-B12/1N	FAZ-B12/3N
13	FAZ-B13/4	FAZ-B13/1N	FAZ-B13/3N
15	FAZ-B15/4	FAZ-B15/1N	FAZ-B15/3N
16	FAZ-B16/4	FAZ-B16/1N	FAZ-B16/3N
20	FAZ-B20/4	FAZ-B20/1N	FAZ-B20/3N
25	FAZ-B25/4	FAZ-B25/1N	FAZ-B25/3N
30	FAZ-B30/4	FAZ-B30/1N	FAZ-B30/3N
32	FAZ-B32/4	FAZ-B32/1N	FAZ-B32/3N
40	FAZ-B40/4	FAZ-B40/1N	FAZ-B40/3N
50	FAZ-B50/4	FAZ-B50/1N	FAZ-B50/3N
63	FAZ-B63/4	FAZ-B63/1N	FAZ-B63/3N

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② Option for single packaging on single-pole B, C and D curves only; add suffix SP when ordering.

FAZ C curve (5–10X I_n current rating)

- Designed for inductive loads
- Response time of instantaneous trip: 5–10X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)
- UL file number 177451

Suitable for applications where medium levels of inrush current are expected. Instantaneous trip is 5–10X rating of device (I_n). Applications include small transformers, lighting, pilot devices, control circuits and coils. Medium magnetic trip point.



Single-Pole

Two-Pole

Three-Pole

C Curve (5–10X I_n Current Rating)—Designed Inductive Loads ①

Amperes	Single-Pole ② Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
0.5	FAZ-C0.5/1-SP	FAZ-C0.5/2	FAZ-C0.5/3
1	FAZ-C1/1-SP	FAZ-C1/2	FAZ-C1/3
1.6	FAZ-C1.6/1-SP	FAZ-C1.6/2	FAZ-C1.6/3
2	FAZ-C2/1-SP	FAZ-C2/2	FAZ-C2/3
3	FAZ-C3/1-SP	FAZ-C3/2	FAZ-C3/3
4	FAZ-C4/1-SP	FAZ-C4/2	FAZ-C4/3
5	FAZ-C5/1-SP	FAZ-C5/2	FAZ-C5/3
6	FAZ-C6/1-SP	FAZ-C6/2	FAZ-C6/3
7	FAZ-C7/1-SP	FAZ-C7/2	FAZ-C7/3
8	FAZ-C8/1-SP	FAZ-C8/2	FAZ-C8/3
10	FAZ-C10/1-SP	FAZ-C10/2	FAZ-C10/3
13	FAZ-C13/1-SP	FAZ-C13/2	FAZ-C13/3
15	FAZ-C15/1-SP	FAZ-C15/2	FAZ-C15/3
16	FAZ-C16/1-SP	FAZ-C16/2	FAZ-C16/3
20	FAZ-C20/1-SP	FAZ-C20/2	FAZ-C20/3
25	FAZ-C25/1-SP	FAZ-C25/2	FAZ-C25/3
30	FAZ-C30/1-SP	FAZ-C30/2	FAZ-C30/3
32	FAZ-C32/1-SP	FAZ-C32/2	FAZ-C32/3
40	FAZ-C40/1-SP	FAZ-C40/2	FAZ-C40/3
50	FAZ-C50/1-SP	FAZ-C50/2	FAZ-C50/3
63	FAZ-C63/1-SP	FAZ-C63/2	FAZ-C63/3

Four-Pole

Single-Pole + Neutral

Three-Pole + Neutral

C Curve (5–10X I_n Current Rating)—Designed Inductive Loads, continued ①

Amperes	Four-Pole Catalog Number	Single-Pole + Neutral Catalog Number	Three-Pole + Neutral Catalog Number
0.5	FAZ-C0.5/4	FAZ-C0.5/1N	FAZ-C0.5/3N
1	FAZ-C1/4	FAZ-C1/1N	FAZ-C1/3N
1.6	FAZ-C1.6/4	FAZ-C1.6/1N	FAZ-C1.6/3N
2	FAZ-C2/4	FAZ-C2/1N	FAZ-C2/3N
3	FAZ-C3/4	FAZ-C3/1N	FAZ-C3/3N
4	FAZ-C4/4	FAZ-C4/1N	FAZ-C4/3N
5	FAZ-C5/4	FAZ-C5/1N	FAZ-C5/3N
6	FAZ-C6/4	FAZ-C6/1N	FAZ-C6/3N
7	FAZ-C7/4	FAZ-C7/1N	FAZ-C7/3N
8	FAZ-C8/4	FAZ-C8/1N	FAZ-C8/3N
10	FAZ-C10/4	FAZ-C10/1N	FAZ-C10/3N
13	FAZ-C13/4	FAZ-C13/1N	FAZ-C13/3N
15	FAZ-C15/4	FAZ-C15/1N	FAZ-C15/3N
16	FAZ-C16/4	FAZ-C16/1N	FAZ-C16/3N
20	FAZ-C20/4	FAZ-C20/1N	FAZ-C20/3N
25	FAZ-C25/4	FAZ-C25/1N	FAZ-C25/3N
32	FAZ-C32/4	FAZ-C32/1N	FAZ-C32/3N
40	FAZ-C40/4	FAZ-C40/1N	FAZ-C40/3N
50	FAZ-C50/4	FAZ-C50/1N	FAZ-C50/3N
63	FAZ-C63/4	FAZ-C63/1N	FAZ-C63/3N

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② Option for single packaging on single-pole B, C and D curves only; add suffix SP when ordering.

1

FAZ D curve (10–20X I_n current rating)

- Designed for highly inductive loads
- Response time of instantaneous trip: 10–20X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)
- UL file number 177451

Suitable for applications where high levels of inrush current are expected. Instantaneous trip is 10–20X rating of device (I_n). The high magnetic trip point prevents nuisance tripping in high inductive applications such as motors, transformers and power supplies.



Single-Pole

Two-Pole

Three-Pole

D Curve (10–20X I_n Current Rating)—Designed for Inductive Loads ①

Amperes	Single-Pole ② Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
0.5	FAZ-D0.5/1-SP	FAZ-D0.5/2	FAZ-D0.5/3
1	FAZ-D1/1-SP	FAZ-D1/2	FAZ-D1/3
2	FAZ-D2/1-SP	FAZ-D2/2	FAZ-D2/3
3	FAZ-D3/1-SP	FAZ-D3/2	FAZ-D3/3
4	FAZ-D4/1-SP	FAZ-D4/2	FAZ-D4/3
5	FAZ-D5/1-SP	FAZ-D5/2	FAZ-D5/3
6	FAZ-D6/1-SP	FAZ-D6/2	FAZ-D6/3
7	FAZ-D7/1-SP	FAZ-D7/2	FAZ-D7/3
8	FAZ-D8/1-SP	FAZ-D8/2	FAZ-D8/3
10	FAZ-D10/1-SP	FAZ-D10/2	FAZ-D10/3
13	FAZ-D13/1-SP	FAZ-D13/2	FAZ-D13/3
15	FAZ-D15/1-SP	FAZ-D15/2	FAZ-D15/3
16	FAZ-D16/1-SP	FAZ-D16/2	FAZ-D16/3
20	FAZ-D20/1-SP	FAZ-D20/2	FAZ-D20/3
25	FAZ-D25/1-SP	FAZ-D25/2	FAZ-D25/3
30	FAZ-D30/1-SP	FAZ-D30/2	FAZ-D30/3
32	FAZ-D32/1-SP	FAZ-D32/2	FAZ-D32/3
40	FAZ-D40/1-SP	FAZ-D40/2	FAZ-D40/3
50 ③	FAZ-D50/1-SP	FAZ-D50/2	FAZ-D50/3
63 ③	FAZ-D63/1-SP	FAZ-D63/2	FAZ-D63/3

Four-Pole

Single-Pole + Neutral

Three-Pole + Neutral

D Curve (10–20X I_n Current Rating)—Designed for Inductive Loads, continued ①

Amperes	Four-Pole Catalog Number	Single-Pole + Neutral Catalog Number	Three-Pole + Neutral Catalog Number
0.5	FAZ-D0.5/4	FAZ-D0.5/1N	FAZ-D0.5/3N
1	FAZ-D1/4	FAZ-D1/1N	FAZ-D1/3N
2	FAZ-D2/4	FAZ-D2/1N	FAZ-D2/3N
3	FAZ-D3/4	FAZ-D3/1N	FAZ-D3/3N
4	FAZ-D4/4	FAZ-D4/1N	FAZ-D4/3N
5	FAZ-D5/4	FAZ-D5/1N	FAZ-D5/3N
6	FAZ-D6/4	FAZ-D6/1N	FAZ-D6/3N
7	FAZ-D7/4	FAZ-D7/1N	FAZ-D7/3N
8	FAZ-D8/4	FAZ-D8/1N	FAZ-D8/3N
10	FAZ-D10/4	FAZ-D10/1N	FAZ-D10/3N
13	FAZ-D13/4	FAZ-D13/1N	FAZ-D13/3N
15	FAZ-D15/4	FAZ-D15/1N	FAZ-D15/3N
16	FAZ-D16/4	FAZ-D16/1N	FAZ-D16/3N
20	FAZ-D20/4	FAZ-D20/1N	FAZ-D20/3N
25	FAZ-D25/4	FAZ-D25/1N	FAZ-D25/3N
30	FAZ-D30/4	FAZ-D30/1N	FAZ-D30/3N
32	FAZ-D32/4	FAZ-D32/1N	FAZ-D32/3N
40	FAZ-D40/4	FAZ-D40/1N	FAZ-D40/3N
50 ③	FAZ-D50/4	FAZ-D50/1N	FAZ-D50/3N
63 ③	FAZ-D63/4	FAZ-D63/1N	FAZ-D63/3N

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② Option for single packaging on single-pole B, C and D curves only; add suffix SP when ordering.

③ IEC 60947-2 only.

FAZ K curve (8–12X I_n current rating)

- Designed for motors, transformers and upstream electronics
- Response time of instantaneous trip: 8–12X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)
- UL file number 177451

Suitable for applications where medium levels of inrush current are expected. Instantaneous trip is 8–12X rating of device (I_n). Applications include small transformers, lighting, pilot devices, control circuits and coils. Medium magnetic trip point.



Single-Pole

Two-Pole

Three-Pole

K Curve (8–12X I_n Current Rating)—Designed for Inductive Loads ①②

Amperes	Single-Pole ③ Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number
0.5	**FAZ-K0.5/1**	**FAZ-K0.5/2**	**FAZ-K0.5/3**
1	**FAZ-K1/1**	**FAZ-K1/2**	**FAZ-K1/3**
1.6	**FAZ-K1.6/1**	**FAZ-K1.6/2**	**FAZ-K1.6/3**
2	**FAZ-K2/1**	**FAZ-K2/2**	**FAZ-K2/3**
3	**FAZ-K3/1**	**FAZ-K3/2**	**FAZ-K3/3**
4	**FAZ-K4/1**	**FAZ-K4/2**	**FAZ-K4/3**
6	**FAZ-K6/1**	**FAZ-K6/2**	**FAZ-K6/3**
8	**FAZ-K8/1**	**FAZ-K8/2**	**FAZ-K8/3**
10	**FAZ-K10/1**	**FAZ-K10/2**	**FAZ-K10/3**
13	**FAZ-K13/1**	**FAZ-K13/2**	**FAZ-K13/3**
16	**FAZ-K16/1**	**FAZ-K16/2**	**FAZ-K16/3**
20	**FAZ-K20/1**	**FAZ-K20/2**	**FAZ-K20/3**
25	**FAZ-K25/1**	**FAZ-K25/2**	**FAZ-K25/3**
32	**FAZ-K32/1**	**FAZ-K32/2**	**FAZ-K32/3**
40	**FAZ-K40/1**	**FAZ-K40/2**	**FAZ-K40/3**
50	**FAZ-K50/1**	**FAZ-K50/2**	**FAZ-K50/3**
63	**FAZ-K63/1**	**FAZ-K63/2**	**FAZ-K63/3**

Four-Pole

Single-Pole + Neutral

Three-Pole + Neutral

K Curve (8–12X I_n Current Rating)—Designed for Inductive Loads, continued ①②

Amperes	Four-Pole ③ Catalog Number	Single-Pole + Neutral Catalog Number	Three-Pole + Neutral Catalog Number
0.5	**FAZ-K0.5/4**	**FAZ-K0.5/1N**	**FAZ-K0.5/3N**
1	**FAZ-K1/4**	**FAZ-K1/1N**	**FAZ-K1/3N**
1.6	**FAZ-K1.6/4**	**FAZ-K1.6/1N**	**FAZ-K1.6/3N**
2	**FAZ-K2/4**	**FAZ-K2/1N**	**FAZ-K2/3N**
3	**FAZ-K3/4**	**FAZ-K3/1N**	**FAZ-K3/3N**
4	**FAZ-K4/4**	**FAZ-K4/1N**	**FAZ-K4/3N**
6	**FAZ-K6/4**	**FAZ-K6/1N**	**FAZ-K6/3N**
8	**FAZ-K8/4**	**FAZ-K8/1N**	**FAZ-K8/3N**
10	**FAZ-K10/4**	**FAZ-K10/1N**	**FAZ-K10/3N**
13	**FAZ-K13/4**	**FAZ-K13/1N**	**FAZ-K13/3N**
16	**FAZ-K16/4**	**FAZ-K16/1N**	**FAZ-K16/3N**
20	**FAZ-K20/4**	**FAZ-K20/1N**	**FAZ-K20/3N**
25	**FAZ-K25/4**	**FAZ-K25/1N**	**FAZ-K25/3N**
32	**FAZ-K32/4**	**FAZ-K32/1N**	**FAZ-K32/3N**
40	**FAZ-K40/4**	**FAZ-K40/1N**	**FAZ-K40/3N**
50	**FAZ-K50/4**	**FAZ-K50/1N**	**FAZ-K50/3N**
63	**FAZ-K63/4**	**FAZ-K63/1N**	**FAZ-K63/3N**

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② These breakers are available by special order and may result in additional delivery time.

③ Two-piece box order, quantities of 2.

1

FAZ S curve (13–17X I_n current rating)

- Designed for control circuits with high inrush
- Response time of instantaneous trip: 13–17X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)
- UL file number 177451

Suitable for applications where high levels of inrush current are expected. Instantaneous trip is 13–17X rating of device (I_n). The high magnetic trip point prevents nuisance tripping in high inductive applications such as motors, transformers and power supplies.



Single-Pole

Two-Pole

S Curve (13–17X I_n Current Rating)—Designed for Inductive Loads ①②

Amperes	Single-Pole ③ Catalog Number	Two-Pole Catalog Number
1	**FAZ-S1/1**	**FAZ-S1/2**
2	**FAZ-S2/1**	**FAZ-S2/2**
3	**FAZ-S3/1**	**FAZ-S3/2**
4	**FAZ-S4/1**	**FAZ-S4/2**
6	**FAZ-S6/1**	**FAZ-S6/2**
10	**FAZ-S10/1**	**FAZ-S10/2**
16	**FAZ-S16/1**	**FAZ-S16/2**
20	**FAZ-S20/1**	**FAZ-S20/2**
25	**FAZ-S25/1**	**FAZ-S25/2**
32	**FAZ-S32/1**	**FAZ-S32/2**
40	**FAZ-S40/1**	**FAZ-S40/2**

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② These breakers are available by special order and may result in additional delivery time.

③ Two-piece box order, quantities of 2.

FAZ Z curve (2–3X I_n current rating)

- Designed for protection of electronic devices
- Response time of instantaneous trip: 2–3X I_n current rating
- UL recognized and CSA Certified as supplementary protectors
- For international and domestic use (conform to IEC 60947-2)

Suitable for applications where low levels of inrush current are expected. Instantaneous trip is 2–3X rating of device (I_n). Applications include small transformers, lighting, pilot devices, control circuits and coils. Medium magnetic trip point.



Single-Pole

Two-Pole

Z Curve (2–3X I_n Current Rating)—Designed for Inductive Loads ①②

Amperes	Single-Pole ③ Catalog Number	Two-Pole Catalog Number
0.5	**FAZ-Z0.5/1**	**FAZ-Z0.5/2**
1	**FAZ-Z1/1**	**FAZ-Z1/2**
1.6	**FAZ-Z1.6/1**	**FAZ-Z1.6/2**
2	**FAZ-Z2/1**	**FAZ-Z2/2**
3	**FAZ-Z3/1**	**FAZ-Z3/2**
4	**FAZ-Z4/1**	**FAZ-Z4/2**
6	**FAZ-Z6/1**	**FAZ-Z6/2**
8	**FAZ-Z8/1**	**FAZ-Z8/2**
10	**FAZ-Z10/1**	**FAZ-Z10/2**
13	**FAZ-Z13/1**	**FAZ-Z13/2**
16	**FAZ-Z16/1**	**FAZ-Z16/2**
20	**FAZ-Z20/1**	**FAZ-Z20/2**
25	**FAZ-Z25/1**	**FAZ-Z25/2**
32	**FAZ-Z32/1**	**FAZ-Z32/2**
40	**FAZ-Z40/1**	**FAZ-Z40/2**
50	**FAZ-Z50/1**	**FAZ-Z50/2**
63	**FAZ-Z63/1**	**FAZ-Z63/2**

Three-Pole

Four-Pole

Z Curve (2–3X I_n Current Rating)—Designed for Inductive Loads, continued ①②

Amperes	Three-Pole Catalog Number	Four-Pole Catalog Number
0.5	**FAZ-Z0.5/3**	**FAZ-Z0.5/4**
1	**FAZ-Z1/3**	**FAZ-Z1/4**
1.6	**FAZ-Z1.6/3**	**FAZ-Z1.6/4**
2	**FAZ-Z2/3**	**FAZ-Z2/4**
3	**FAZ-Z3/3**	**FAZ-Z3/4**
4	**FAZ-Z4/3**	**FAZ-Z4/4**
6	**FAZ-Z6/3**	**FAZ-Z6/4**
8	**FAZ-Z8/3**	**FAZ-Z8/4**
10	**FAZ-Z10/3**	**FAZ-Z10/4**
13	**FAZ-Z13/3**	**FAZ-Z13/4**
16	**FAZ-Z16/3**	**FAZ-Z16/4**
20	**FAZ-Z20/3**	**FAZ-Z20/4**
25	**FAZ-Z25/3**	**FAZ-Z25/4**
32	**FAZ-Z32/3**	**FAZ-Z32/4**
40	**FAZ-Z40/3**	**FAZ-Z40/4**
50	**FAZ-Z50/3**	**FAZ-Z50/4**
63	**FAZ-Z63/3**	**FAZ-Z63/4**

Notes

① In North America, these switches are UL recognized and CSA Certified as supplementary protection devices. Per the intent of NEC (National Electrical Code), Article 240, and CEC (Canadian Electrical Code), Part 1 C22.1, supplementary breakers cannot be used as a substitute for the branch circuit protective device. They can be used to provide overcurrent protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

② These breakers are available by special order and may result in additional delivery time.

③ Two-piece box order, quantities of 2.

1

Accessories

FAZ Auxiliary Contacts and Voltage Trips

	Circuit Diagram	Description	Rated Operational Voltage	Catalog Number
Standard Auxiliary Contacts				
		■ 1NO/1NC ■ Installs on left side of FAZ or shunt trip ■ Max. one per FAZ (1077) device ■ Switches when FAZ is tripped electrically or manually	230 Vac	**FAZ-XHIN11**
		■ 1 changeover contact ■ Installs on left side of FAZ or shunt trip ■ Max. one per FAZ (1077) device ■ Switches when FAZ is tripped electrically or manually	230 Vac	**FAZ-XHINW1**
Auxiliary/Trip Indicating Contact				
	 Two-pole auxiliary mode  Trip indicating mode	■ Small selector screw changes mode ■ Two Form C (changeover) contacts ■ Installs on left side of FAZ or shunt trip ■ Auxiliary contacts switch when FAZ is tripped electrically or manually ■ Trip indicating contact switches only when FAZ is tripped electrically	230 Vac	**FAZ-XAM002**
Undervoltage Trip				
		■ Prevents FAZ from operating unless voltage is present ■ Installs on left side of FAZ ■ Includes test button	115 Vac 230 Vac 400 Vac	**FAZ-XUA(115VAC)** **FAZ-XUA(230VAC)** **FAZ-XUA(400VAC)**
Shunt Trip				
		■ Allows remote trip of FAZ ■ Installs on left side of FAZ	12–110 Vac 12–60 Vdc 110–415 Vac 110–230 Vdc	**FAZ-XAA-C-12-110VAC** **FAZ-XAA-C-110-415VAC**

Allowable Combinations of Accessories



Busbar System

Description	Rated Operational Current	Number of Poles per Device	Number of Terminals	Catalog Number ①
Without Auxiliary Contacts				
For connecting FAZ supplementary protectors without auxiliary contacts. May be fed from line or load side.	80A	1	57	**BB-UL-18/1P-1M/57**
		2	56	**BB-UL-18/2P-2M/56**
		3	57	**BB-UL-18/3P-3M/57**
	100A	1	57	**BB-UL-25/1P-1M/57**
		2	56	**BB-UL-25/2P-2M/56**
		3	57	**BB-UL-25/3P-3M/57**
Auxiliary/Trip Indicating Contacts				
For connecting FAZ supplementary protectors with auxiliary contacts. May be fed from line or load side.	80A	1	37	**BB-UL-18/1P-1,5M/37**
		2	46	**BB-UL-18/2P+AS-2,5M/46**
		3	48	**BB-UL-18/3P+AS-3,5M/48**
	100A	1	37	**BB-UL-25/1P-1,5M/37**
		2	46	**BB-UL-25/2P+AS-2,5M/46**
		3	48	**BB-UL-25/3P+AS-3,5M/48**





Note

① Bus may be center fed for high current capacity.



Incoming Terminal



Pin Type Incoming Supply Terminals

Description	Catalog Number
■ Accommodates conductors from 6–35 mm^2/#10–2 AWG ■ 4–5.5 Nm/35–50 lb-in ■ Two- and three-pole	**BB-UL-TEP/35**

Incoming Terminal

Pin Type Incoming Supply Terminals—Single-Phase Only

Description	Catalog Number
■ Accommodates conductors from 6–35 mm^2/#10–2 AWG ■ 4–5.5 Nm/35–50 lb-in	**BB-UL-TEPA/35**

Protective Accessories

Busbar Terminal Cover



Description	Catalog Number
For covering unused terminals	**BB-IP/5**

Lockoff Device



UL lockoff device	**FAZPLOFF**

Padlock Hasp



■ Prevents reactivation of the device during maintenance ■ Holds one padlock	**Z-IS/SPE-1TE**

Incoming Terminal



Bus Incoming Supply Terminals

Description	Catalog Number
■ 50 mm^2 ■ #14–1 AWG ■ 75 Deg wire ■ 115 A/Y, 480V UL ■ 160 A/Y 690V IEC	**BB-UL-TE/50**

Fork Connector





Busbar End Cap

Description	Poles	Catalog Number
■ Install after cutting busbar ■ Protects end of busbar	2 and 3	**BB-EV-EC/3**
	1	**BB-UL-EC/1**

Technical Data and Specifications

Trip Curves Chart

Eaton FAZ supplementary protectors are available with six different tripping characteristics, including Type B, C, D, K, S and Z. Definitions for each trip curve are contained on the ordering pages and can be used to determine the optimal characteristic for your application. For example, low-level short-circuit faults in control wiring, such as PLCs, are best protected by devices with Type B trip characteristics (3–5X continuous rating of the device (I_n).

Even though not required by NEC or CEC for supplementary protectors, Eaton's FAZ devices are current limiting, which means that they interrupt fault currents within one half cycle. Current limiting devices offer superior protection by reducing peak let-through current and energy.

Tripping Characteristics



FAZ Miniature Circuit Breakers Technical Data

Description	B Curve	C Curve	D Curve
Electrical			
Approvals	UR (UL 1077), CSA (CSA 22.2 No. 235), CE		
Standards	IEC/EN 60947-2		
Short-circuit trip response	3–5 I_n	5–10 I_n	10–20 I_n
Supplementary Protectors—UL/CSA			
Current range	1–63A	0.5–63A	0.5–40A
Maximum voltage ratings—UL/CSA			
Single-pole, single-pole + neutral	277 Vac 48 Vdc	277 Vac 48 Vdc	277 Vac 48 Vdc
Two-, three-pole, four-pole and three-pole + neutral	480Y/277 Vac	480Y/277 Vac	480Y/277 Vac
Two poles in series	96 Vdc	96 Vdc	96 Vdc
Thermal tripping characteristics			
Single-pole	1.35 x I_n @ 40°C	1.35 x I_n @ 40°C	1.35 x I_n @ 40°C
Multi-pole	1.45 x I_n @ 40°C	1.45 x I_n @ 40°C	1.45 x I_n @ 40°C
Short-circuit ratings (at max. voltage)			
Single-pole	10 kA (5 kA for 40–63A device)	10 kA (5 kA for 40–63A device)	5 kA
Two-, three-pole	10 kA (5 kA for 40–63A device)	10 kA (5 kA for 40–63A device)	5 kA
Single-pole	10 kA @ 48 Vdc	10 kA @ 48 Vdc	10 kA @ 48 Vdc
Two poles in series	10 kA @ 96 Vdc	10 kA @ 96 Vdc	10 kA @ 96 Vdc
Miniature Circuit Breaker—IEC			
Current range	1–63A	0.5–63A	0.5–63A
Maximum voltage ratings—IEC 68898-1			
Single-pole	230 Vac	230 Vac	230 Vac
Two-, three-pole	230/400 Vac	230/400 Vac	230/400 Vac
Maximum voltage ratings—IEC 60947-2			
Single-pole	240 Vac 48 Vdc	240 Vac 48 Vdc	240 Vac 48 Vdc
Two-, three-pole	240/415 Vac	240/415 Vac	240/415 Vac
Two poles in series	96 Vdc	96 Vdc	96 Vdc
Thermal tripping characteristics			
Single-pole	> 1 hour @ 1.05 x I_n	> 1 hour @ 1.05 x I_n	> 1 hour @ 1.05 x I_n
Multi-pole	< 1 hour @ 1.3 x I_n	< 1 hour @ 1.3 x I_n	< 1 hour @ 1.3 x I_n
Interrupt ratings (at max. voltage)			
IEC 60947-2	15 kA	15 kA	15 kA (10 kA for 50 and 63A)
IEC 60898	10 kA	10 kA	10 kA (50 and 63A not available)
Operational switching capacity	7.5 kA	7.5 kA	7.5 kA
Max. backup fuse [gL/gG]	125A	125A	125A
Rated impulse withstand—U_{imp}	4000 Vac	4000 Vac	4000 Vac
Rated insulation voltage—U_i	440 Vac	440 Vac	440 Vac
Environmental/General			
Selectivity class	3	3	3
Lifespan (operations)	> 10,000 (1 operation = ON/OFF)	> 10,000 (1 operation = ON/OFF)	> 10,000 (1 operation = ON/OFF)
Shock (IEC 68-2-22)	10g–120 ms	10g–120 ms	10g–120 ms
Operating temperature range	–40 to +167°F (–40 to +75°C)	–40 to +167°F (–40 to +75°C)	–40 to +167°F (–40 to +75°C)
Shipment and short-term storage	–40 to +185°F (–40 to +85°C)	–40 to +185°F (–40 to +85°C)	–40 to +185°F (–40 to +85°C)
Housing material	Nylon	Nylon	Nylon
Mechanical			
Standard front dimension			
Device height	80 mm	80 mm	80 mm
Terminal protection	Finger and back-of-hand proof to IEC 536	Finger and back-of-hand proof to IEC 536	Finger and back-of-hand proof to IEC 536
Mounting width per pole	17.5 mm	17.5 mm	17.5 mm
Mounting	IEC/EN 60715 top-hat rail	IEC/EN 60715 top-hat rail	IEC/EN 60715 top-hat rail
Degree of protection	IP20	IP20	IP20
Terminals top and bottom	Twin-purpose terminals	Twin-purpose terminals	Twin-purpose terminals
Supply connection	Line or load side	Line or load side	Line or load side
Terminal capacity [mm^2]	1 x 25 (AWG 4–18)/2 x 10 (AWG 8–18)	1 x 25 (AWG 4–18)/2 x 10 (AWG 8–18)	1 x 25 (AWG 4–18)/2 x 10 (AWG 8–18)
Torque	2.4 Nm	2.4 Nm	2.4 Nm
Imperial torque	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)
Thickness of busbar material	0.8–2 mm	0.8–2 mm	0.8–2 mm
Mounting position	As required	As required	As required

FAZ Miniature Circuit Breakers Technical Data, continued

Description	K Curve	S Curve	Z Curve
Electrical			
Approvals	UR (UL 1077), CSA (CSA 22.2 No. 235), CE		
Standards	IEC/EN 60947-2, E177451, 204453		
Short-circuit trip response	8–12 I_n	13–17 I_n	2–3 I_n
Supplementary Protectors—UL/CSA			
Current range	0.5–63A	0.5–40A	1–63A
Maximum voltage ratings—UL/CSA			
Single-pole, single-pole + neutral	277 Vac 48 Vdc	277 Vac 48 Vdc	277 Vac 48 Vdc
Two-, three-, four-pole and three-pole + neutral	480Y/277 Vac	480Y/277 Vac	480Y/277 Vac
Two poles in series	96 Vdc	96 Vdc	96 Vdc
Thermal tripping characteristics			
Single-pole	1.35 x I_n @ 40°C	1.35 x I_n @ 40°C	1.35 x I_n @ 40°C
Multi-pole	1.45 x I_n @ 40°C	1.45 x I_n @ 40°C	1.45 x I_n @ 40°C
Short-circuit ratings (at max. voltage)			
Single-pole	5 kA @ 277 Vac	5 kA @ 277 Vac	5 kA @ 277 Vac
Single-pole + neutral	5 kA @ 277 Vac	5 kA @ 277 Vac	5 kA @ 277 Vac
Two-, three-, four-pole	5 kA @ 480Y/277 Vac	5 kA @ 480Y/277 Vac	5 kA @ 480Y/277 Vac
Two poles in series	—	—	—
Miniature Circuit Breaker—IEC			
Current range	0.5–63A	0.5–40A	1–63A
Maximum voltage ratings—IEC 60947-2			
Single-pole, single-pole + neutral	240 Vac	240 Vac	240 Vac
Two-, three-, four-pole, three-pole + neutral	240/415 Vac	240/415 Vac	240/415 Vac
Thermal tripping characteristics			
Single-pole	> 1 Hour @ 1.05 x I_n	> 1 Hour @ 1.05 x I_n	> 1 Hour @ 1.05 x I_n
Multi-pole	< 1 Hour @ 1.3 x I_n	< 1 Hour @ 1.3 x I_n	< 1 Hour @ 1.3 x I_n
Interrupt ratings (at max. voltage)			
IEC 60947-2	15 kA	10 kA	10 kA
Operational switching capacity	7.5 kA	7.5 kA	7.5 kA
Max. backup fuse [gL/gG]	125A	125A	125A
Rated impulse withstand—U_{imp}	4000 Vac	4000 Vac	4000 Vac
Rated insulation voltage—U_i	440 Vac	440 Vac	440 Vac
Environmental/General			
Selectivity class	3	3	3
Lifespan (operations)	> 10,000 (1 operation = ON/OFF)	> 10,000 (1 operation = ON/OFF)	> 10,000 (1 operation = ON/OFF)
Shock (IEC 68-2-22)	10g–120 ms	10g–120 ms	10g–120 ms
Operating temperature range	–40 to +167°F (–40 to +75°C)	–40 to +167°F (–40 to +75°C)	–40 to +167°F (–40 to +75°C)
Shipment and short-term storage	–40 to +185°F (–40 to +85°C)	–40 to +185°F (–40 to +85°C)	–40 to +185°F (–40 to +85°C)
Housing material	Nylon	Nylon	Nylon
Mechanical			
Standard front dimension			
Device height	80 mm	80 mm	80 mm
Terminal protection	Finger and back-of-hand proof to IEC 536	Finger and back-of-hand proof to IEC 536	Finger and back-of-hand proof to IEC 536
Mounting width per pole	17.7 mm	17.7 mm	17.7 mm
Mounting	IEC/EN 60715 top-hat rail	IEC/EN 60715 top-hat rail	IEC/EN 60715 top-hat rail
Degree of protection	IP20	IP20	IP20
Terminals top and bottom	Twin-purpose terminals	Twin-purpose terminals	Twin-purpose terminals
Supply connection	Line or load side	Line or load side	Line or load side
Terminal capacity [mm^2]	1 x 25 (AWG 4–18) / 2 x 10 (AWG 8–18)	1 x 25 (AWG 4–18) / 2 x 10 (AWG 8–18)	1 x 25 (AWG 4–18) / 2 x 10 (AWG 8–18)
Torque	2.4 Nm	2.4 Nm	2.4 Nm
Imperial torque	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)	21 lb-in (AWG 18–12), 25 lb-in (AWG 10–8), 36 lb-in (AWG 6–4)
Thickness of busbar material	0.8–2 mm	0.8–2 mm	0.8–2 mm
Mounting position	As required	As required	As required

1

Let-Through Energy I^2t

Characteristic B and C



Characteristic D



Let-Through Energy I_D

Characteristic B and C



Characteristic D



Let-Through Energy I^2t

Characteristic K



Characteristic S



Characteristic Z



Influence of the Ambient Temperature on the Thermal Tripping Behavior

Corrected values of the rated current dependent on the ambient temperature

	Ambient Temperature T																
I_n (A)	–40°C	–30°C	–20°C	–10°C	0°C	10°C	20°C	30°C	35°C	40°C	45°C	50°C	55°C	60°C	65°C	70°C	75°C
0.16	0.20	0.20	0.19	0.19	0.18	0.17	0.17	0.16	0.16	0.15	0.15	0.15	0.14	0.14	0.14	0.14	0.13
0.25	0.32	0.31	0.30	0.29	0.28	0.27	0.26	0.25	0.25	0.24	0.24	0.23	0.23	0.22	0.22	0.21	0.21
0.50	0.64	0.62	0.60	0.58	0.56	0.54	0.52	0.50	0.49	0.48	0.47	0.46	0.45	0.44	0.43	0.42	0.41
0.75	0.96	0.93	0.90	0.87	0.84	0.81	0.78	0.75	0.74	0.73	0.71	0.69	0.68	0.66	0.65	0.64	0.62
1.00	1.30	1.20	1.20	1.20	1.10	1.10	1.00	1.00	0.99	0.97	0.95	0.93	0.90	0.89	0.87	0.85	0.83
1.50	1.90	1.90	1.80	1.70	1.70	1.60	1.60	1.50	1.50	1.50	1.40	1.40	1.40	1.30	1.30	1.30	1.20
1.60	2.00	2.00	1.90	1.90	1.80	1.70	1.70	1.60	1.60	1.50	1.50	1.50	1.40	1.40	1.40	1.40	1.30
2.00	2.60	2.50	2.40	2.30	2.20	2.20	2.10	2.00	2.00	1.90	1.90	1.90	1.80	1.80	1.70	1.70	1.70
2.50	3.20	3.10	3.00	2.90	2.80	2.70	2.60	2.50	2.50	2.40	2.40	2.30	2.30	2.20	2.20	2.10	2.10
3.00	3.80	3.70	3.60	3.50	3.40	3.30	3.10	3.00	3.00	2.90	2.80	2.80	2.70	2.70	2.60	2.50	2.50
3.50	4.50	4.40	4.20	4.10	3.90	3.80	3.70	3.50	3.40	3.40	3.30	3.20	3.20	3.10	3.00	3.00	2.90
4.00	5.10	5.00	4.80	4.70	4.50	4.30	4.20	4.00	3.90	3.90	3.80	3.70	3.60	3.50	3.50	3.40	3.30
5.00	6.40	6.20	6.00	5.80	5.60	5.40	5.20	5.00	4.90	4.80	4.70	4.60	4.50	4.40	4.30	4.20	4.10
6.00	7.70	7.50	7.20	7.00	6.70	6.50	6.30	6.00	5.90	5.80	5.70	5.60	5.40	5.30	5.20	5.10	5.00
7.00	9.00	8.70	8.40	8.20	7.80	7.60	7.40	7.00	6.90	6.80	6.70	6.50	6.30	6.20	6.10	6.00	5.80
8.00	10.20	9.90	9.60	9.30	9.00	8.70	8.40	8.00	7.90	7.70	7.60	7.40	7.20	7.10	6.90	6.80	6.60
10.00	13.00	12.00	12.00	12.00	11.00	11.00	10.00	10.00	9.90	9.70	9.50	9.30	9.00	8.90	8.70	8.50	8.30
12.00	15.00	15.00	14.00	14.00	13.00	13.00	13.00	12.00	12.00	12.00	11.00	11.00	11.00	11.00	10.00	10.00	10.00
13.00	17.00	16.00	16.00	15.00	15.00	14.00	14.00	13.00	13.00	13.00	12.00	12.00	12.00	12.00	11.00	11.00	11.00
15.00	19.00	19.00	18.00	17.00	17.00	16.00	16.00	15.00	15.00	15.00	14.00	14.00	14.00	13.00	13.00	13.00	12.00
16.00	20.00	20.00	19.00	19.00	18.00	17.00	17.00	16.00	16.00	15.00	15.00	15.00	14.00	14.00	14.00	14.00	13.00
20.00	26.00	25.00	24.00	23.00	22.00	22.00	21.00	20.00	20.00	19.00	19.00	19.00	18.00	18.00	17.00	17.00	17.00
25.00	32.00	31.00	30.00	29.00	28.00	27.00	26.00	25.00	25.00	24.00	24.00	23.00	23.00	22.00	22.00	21.00	21.00
32.00	41.00	40.00	38.00	37.00	36.00	35.00	33.00	32.00	32.00	31.00	30.00	30.00	29.00	28.00	28.00	27.00	26.00
35.00	45.00	43.00	41.00	41.00	38.00	38.00	36.00	35.00	35.00	34.00	33.00	32.00	32.00	32.00	30.00	29.00	29.00
40.00	51.00	50.00	48.00	47.00	45.00	43.00	42.00	40.00	39.00	39.00	38.00	37.00	36.00	35.00	35.00	34.00	33.00
50.00	64.00	62.00	60.00	58.00	56.00	54.00	52.00	50.00	49.00	48.00	47.00	46.00	45.00	44.00	43.00	42.00	41.00
63.00	81.00	78.00	76.00	73.00	71.00	68.00	66.00	63.00	62.00	61.00	60.00	58.00	57.00	56.00	55.00	53.00	52.00

Influence of the Mains Frequency

Influence of the mains frequency on the tripping behavior I_{MA} of the instantaneous release

	Mains Frequency f [Hz]						
	16 2/3	50	60	100	200	300	400
$I_{MA}(f)/I_{MA}$ (50 Hz) [%]	91	100	101	106	115	134	141

Load Carrying Capacity of Adjoining Miniature Circuit Breakers



Accessories Technical Data

Description	FAZ-XHIN FAZ-XAM002	FAZ-XAA-C	FAZ-XUA
Electrical			
Contact function	1A + 1B 2 C/O	— —	— —
Rated operational voltage U_n	250 Vac	—	115 Vac 230 Vac 400 Vac
Voltage range	—	12–110 Vac 12–60 Vdc	—
Voltage range	—	110–415 Vac 110–230 Vdc	—
Closing threshold [x U_n]	—	—	0.8
Tripping threshold [x U_n]	—	—	0.5
Rated frequency f	50/60 Hz	50/60 Hz	50/60 Hz
General use (UL/CSA) AC—230/240 Vac DC—110/120 Vdc	 2/2A 0.5/0.5A	 — —	 — —
Pilot duty	A600/Q600	—	—
Conventional free air thermal current I_{th}	4A	—	—
Rated operational current AC-13 I_e AC-15 I_e DC-13 I_e	 3A (250 Vac) 2A (250 Vac) 0.5A (110 Vdc)	 — — —	 — — —
Rated insulation voltage U_i	250 Vac	—	—
Minimum operating voltage per contract U_{min}	5 Vdc	—	—
Rated impulse withstand voltage (1.2/50µ) U_{imp}	2.5 kV	—	—
Rated conditional short-circuit current with 6A backup fuse I_{SC}	1 kA	—	—
Max. admissible backup fuse	4A gL	—	—
Mechanical			
Standard front dimension	45 mm	45 mm	45 mm
Device height	80 mm	80 mm	80 mm
Mounting width	8.8 mm	17.6 mm	17.8 mm
Mounting	On MCB	IEC/EN 60715 top-hat rail	IEC/EN 60715 top-hat rail
Degree of protection enclosed	IP40	IP40	IP40
Terminal protection	Protection against electric shock to IEC 536	Protection against electric shock to IEC 536	Protection against electric shock to IEC 536
Terminals	Lift terminals	Twin-purpose terminals	Twin-purpose terminals
Terminal capacity Solid Flexible	 0.5–2.5 mm^2 0.5–2.5 mm^2	 1–2.5 mm^2 1–2.5 mm^2	 2 x (1–2.5) mm^2 2 x (1–2.5) mm^2
Tightening torque of terminal screws	0.8–1.0 Nm (7–9 lb-in)	2.4 Nm (21 lb-in)	0.8 Nm (7 lb-in)

1

Dimensions

Approximate Dimensions in Inches (mm)

Miniature Circuit Breakers

FAZ



Auxiliary Contacts

FAZ-XHI11 and FAZ-XH1NW1



FAZ-XAM002



Shunt Releases

FAZ-XAA



Undervoltage Releases

FAZ-XUA



Approximate Dimensions in Inches (mm)

Busbar and Accessory Weights and Dimensions

Unit Weight (kg)	Length	Width	Height	Catalog Number
0.29	39.72 (1009.0)	0.59 (15.0)	0.59 (15.0)	**BB-UL-18/1P-1M/57**
0.64	39.02 (991.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-18/2P-2M/56**
0.83	39.72 (1009.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-18/3P-3M/57**
0.26	38.78 (985.0)	0.59 (15.0)	0.59 (15.0)	**BB-UL-18/1P-1.5M/37**
0.63	39.72 (1009.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-18/2P+AS-2.5M/46**
0.79	38.66 (982.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-18/3P+AS-3.5M/48**
0.36	39.72 (1009.0)	0.59 (15.0)	0.59 (15.0)	**BB-UL-25/1P-1M/57**
0.79	39.02 (991.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-25/2P-2M/56**
1.04	39.72 (1009.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-25/3P-3M/57**
0.31	38.78 (985.0)	0.59 (15.0)	0.59 (15.0)	**BB-UL-25/1P-1.5M/37**
0.73	39.72 (1009.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-25/2P+AS-2.5M/46**
0.97	38.66 (982.0)	0.87 (22.0)	1.46 (37.0)	**BB-UL-25/3P+AS-3.5M/48**
0.03	2.36 (60.0)	0.67 (17.0)	1.14 (29.0)	**BB-UL-TEP/35**
0.03	1.42 (36.0)	0.67 (17.0)	1.14 (29.0)	**BB-UL-TEPA/35**
0.03	1.57 (40.0)	0.71 (18.0)	1.18 (30.0)	**BB-UL-TE/50**
0.003	3.35 (85.0)	0.47 (12.0)	0.94 (24.0)	**BB-IP/5**
0.001	0.55 (14.0)	0.20 (5.0)	0.39 (10.0)	**BB-EV-EC/3**
0.001	0.94 (24.0)	0.87 (22.0)	0.39 (10.0)	**BB-UL-EC/1**





Contents

Description	*Page*
UL 1053 DIN Rail RCCB 480/277 Vac	
Product Selection	**V4-T1-91**
Accessories	**V4-T1-92**
Technical Data and Specifications	**V4-T1-93**
Dimensions	**V4-T1-94**
UL 1053 DIN Rail RCCB 208Y/120 Vac	**V4-T1-96**

UL 1053 DIN Rail RCCB 480/277 Vac

Product Overview

Optimum product quality, tested reliability and safety stand for best protection of installations and plant. Eaton's UL 1053 Residual Current Circuit Breaker (RCCB) is designed for use in residual current applications.

Application Description

- Motor control circuits
- HVAC internal/external equipment
- PLCs
- HMIs
- Equipment protection
- European housing

Features

- Wide range of compact RCCB types serving as fault-current and additional protection according to UL 1053 and IEC/EN 61008 standards, suitable for worldwide use
- Type A or Type G/A (with delay) protection available
- Comprehensive range of accessories
- Real contact position indicator
- Fault current tripping indicator
- Transparent designation plate
- Trip-free design—RCCB can not be defeated by holding the handle in the ON position
- Captive screws cannot be lost

Standards and Certifications

- UL 1053
- IEC/EN 61008
- CSA
- ÖVE
- CE Marked

Listed

Product Selection

UL 1053 RCCB 480Y/277V Type A

Two-Pole

Conditionally Surge Current–Proof 250A, Sensitive to Residual Pulsating DC, Type A

Two-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167113**	FRCmM-25/2/003-A-NA
	300	**167116**	FRCmM-25/2/03-A-NA
40	30	**167114**	FRCmM-40/2/003-A-NA
	300	**167117**	FRCmM-40/2/03-A-NA
63	30	**167115**	FRCmM-63/2/003-A-NA
	300	**167118**	FRCmM-63/2/03-A-NA

Four-Pole

Conditionally Surge Current–Proof 250A, Sensitive to Residual Pulsating DC, Type A

Four-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167125**	FRCmM-25/4/003-A-NA
	300	**167104**	FRCmM-25/4/03-A-NA
40	30	**167102**	FRCmM-40/4/003-A-NA
	300	**167105**	FRCmM-40/4/03-A-NA
63	30	**167103**	FRCmM-63/4/003-A-NA
	300	**167106**	FRCmM-63/4/03-A-NA

UL 1053 RCCB 480Y/277V Type G/A

Type G/A has a 10 ms delay.

Two-Pole

Surge Current–Proof 3 kA, Sensitive to Residual Pulsating DC, Type G/A (ÖVE E 8601)

Two-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167119**	FRCmM-25/2/003-G/A-NA
	300	**167122**	FRCmM-25/2/03-G/A-NA
40	30	**167120**	FRCmM-40/2/003-G/A-NA
	300	**167123**	FRCmM-40/2/03-G/A-NA
63	30	**167121**	FRCmM-63/2/003-G/A-NA
	300	**167124**	FRCmM-63/2/03-G/A-NA

Four-Pole

Surge Current–Proof 3 kA, Sensitive to Residual Pulsating DC, Type G/A (ÖVE E 8601)

Four-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167107**	FRCmM-25/4/003-G/A-NA
	300	**167110**	FRCmM-25/4/03-G/A-NA
40	30	**167108**	FRCmM-40/4/003-G/A-NA
	300	**167111**	FRCmM-40/4/03-G/A-NA
63	30	**167109**	FRCmM-63/4/003-G/A-NA
	300	**167112**	FRCmM-63/4/03-G/A-NA

Note

① Has no thermal element; must be paired with FAZ-NA or FAZ per application.

1

Accessories

UL 1053 DIN Rail RCCB 480/277 Vac

Contact

Description	Catalog Number
Two-pole contact or auxiliary contact / trip indicating contact	**Z-NHK** ①

Padlock Hasp



Description	Catalog Number
Padlock hasp	**Z-IS/SPE-1TE**

Lockoff Device



Description	Catalog Number
UL lockoff device	**FAZPLOFF**

Note

① Voltage of FAZ-NA circuit breaker is limited to 300V with this auxiliary contact installed.

Technical Data and Specifications

- Residual current devices
- Has no thermal protection; must be paired with FAZ-NA or FAZ per application
- Captive screw terminals
- Universal tripping signal switch, also suitable for Z-A; can be mounted subsequently
- Auxiliary switch Z-HK can be mounted subsequently
- Red-green contact position indicator
- White-blue tripping indicator
- Delayed types recommended for use with standard fluorescent tubes with or without electronical ballast (30mA-RCD: 30 units per phase conductor, 100mA-RCD: 90 units per phase conductor)
- The device functions irrespective of the position of installation
- Tripping is line voltage-independent. Consequently, the RCD is suitable for "fault current/residual current protection" and "additional protection" within the meaning of the applicable installation rules
- Reverse-feed permitted
- The four-pole device can also be used for two-pole connection. For this purpose, use terminals 5-6 and N-N
- The test key "T" must be pressed every month. The system operator must be informed of this obligation and responsibility in a way that can be proven (self-adhesive RCD-label enclosed)
- Pressing the test key "T" serves the only purpose of function testing the residual current device (RCD). This test does not make earthing resistance measurement (RE) or proper checking of the earth conductor condition redundant, which must be performed separately
- **Type -A:** Protects against special forms of residual pulsating DC that have not been smoothed
- **Type -G/A:** Additionally protects against special forms of residual pulsating DC that have not been smoothed

UL 1053 DIN Rail RCCB Technical Data

Description	Specification	
Electrical According to IEC/EN 61008		
Design according to	IEC/EN 61008	
	ÖVE E 8601	
Current test marks as printed onto the device		
Tripping Type G	10 ms delay	
Rated voltage U_n	230/400V, 50 Hz	
Rated tripping current $I_{\Delta n}$	30, 300 mA	
Sensitivity	AC and pulsating DC	
Rated insulation voltage U_i	440V	
Rated impulse withstand voltage U_{imp}	4 kV	
Rated short-circuit capacity I_{nc}	10 kA	
Maximum backup fuse	Overload protection	Short-circuit protection
I_n = 25–40A	25A gG/gL	63A gG/gL
I_n = 63A	40A gG/gL	63A gG/gL
Rated breaking capacity I_m bzw. Rated fault breaking capacity $I_{\Delta m}$		
I_n = 25–40A	500A	
I_n = 63A	630A	
Voltage range of test button	Two-pole	184–250V~
	Four-pole	184–440V~
Endurance	Electrical	>4000 operating cycles
	Mechanical	>20,000 operating cycles
Overvoltage category	III	

UL 1053 DIN Rail RCCB Technical Data, continued

Description	Specification	
Electrical According to UL 1053		
Design according to	UL 1053	
Current test marks as printed onto the device		
Tripping Type G	8 ms delay	
Rated voltage U_n	480Y/277V, 60 Hz	
Pickup current	22, 200 mA	
Sensitivity	AC and pulsating DC	
Overvoltage tested	530V	
Rated impulse withstand voltage U_{imp}	4 kV	
Rated short-circuit capacity I_{nc}	5 kA according to CSA	
Maximum backup fuse	Overload protection	Short-circuit protection
I_n = 25–40A	25A gG/gL	63A gG/gL
I_n = 63A	40A gG/gL	63A gG/gL
Rated breaking capacity I_m or Rated fault breaking capacity $I_{\Delta m}$		
I_n = 25–40A	500A	
I_n = 63A	630A	
Voltage range of test button	Two-pole	184–305V~
	Four-pole	184–528V~
Endurance	Electrical	>4000 operating cycles
	Mechanical	>20,000 operating cycles
Mechanical		
Frame size	45.0 mm	
Device height	80.0 mm	
Device width	35 mm (2TE), 70 mm (4TE)	
Device width	Quick fastening with two lock-in positions on DIN rail IEC/EN 60715	
Degree of protection, built-in	IP40	
Degree of protection in moisture-proof enclosure	IP54	
Upper and lower terminals	Lift terminals	
Terminal protection	Finger and hand touch safe BGV A3, ÖVE-EN 6	
Terminal capacity	1.5–35 mm^2 single-wire	
	2 x 16 mm^2 multi-wire	
Busbar material thickness	0.8–2 mm	
Tripping temperature	–25°C to +60°C	
Resistance to climatic conditions	According to IEC 61008	
Humidity	5–95%	

Connection Diagram



Two-Pole



Four-Pole

Impact of Ambient Temperature on the Maximum Permanent Current Allowed (A)

Tripping Temperature	16A Two-Pole	16A Four-Pole	25A Two-Pole	25A Four-Pole	40A Two-Pole	40A Four-Pole	63A Two-Pole	63A Four-Pole
40°C	16	16	25	25	40	40	63	63
45°C	14	14	21	22	37	37	59	59
50°C	11	11	18	19	33	34	55	55
55°C	9	9	14	16	30	31	50	50
60°C	①	—	—	—	26	27	45	45

Notes

① Do not use.

Please make sure that these values are not exceeded and that any upstream overload protection switches off in time.

Correct Connection



3+N
(230/400V) IEC
(277/480V) UL



Three-phase load without N
(184–254 Vac Phase-Phase) IEC
(184–277 Vac Phase-Phase) UL



Three-phase load without N
(400 Vac Phase-Phase) IEC
(480 Vac Phase-Phase) UL



1+N
(230V) IEC
(277V) UL

Dimensions

Approximate Dimensions in Inches (mm)

UL 1053 DIN Rail RCCB



Four-Pole

Accessories Technical Data

Description	Z-NHK
Electrical	
Contact function	2CO
Rated voltage	230V
Frequency	50/60 Hz
Rated current	2A
Rated thermal current I_{th}	2A
Utilization category AC13 Rated operational current I_e	3A/250 Vac
Utilization category AC15 Rated operational current I_e	2A/250 Vac
Utilization category DC12 Rated operational current I_e	0.5A/110 Vdc
Rated insulation voltage U_i	250 Vac
Minimum operational voltage per contact U_{min}	5 Vdc
Minimum operational current I_{min}	10 mA DC
Rated peak withstand voltage U_{imp} (1.2/50µ)	2.5 kV
Conditional short-circuit current I_k with backup fuse 6A	1 kA
Maximum backup fuse, overload and short circuit	6A gL
Mechanical	
Tripping indicator “electrical tripping”	Blue/white
Frame size	45 mm
Device height	80 mm
Device width	8.8 mm (0.5MU)
Mounting	Onto switching device
Degree of protection, built-in	IP40
Terminal protection	Finger and hand touch safe According to BGV A3, ÖVE-EN 6
Terminals	Lift terminals
Terminal capacity	20–14 AWG
Terminal screws	M3 (Posidrive Z0)
Fastening torque of terminal screws	7 lb-in maximum

UL 1053 DIN Rail RCCB

Contents

Description	*Page*
UL 1053 DIN Rail RCCB 480/277 Vac	**V4-T1-90**
UL 1053 DIN Rail RCCB 208Y/120 Vac	
Product Selection	**V4-T1-97**
Accessories	**V4-T1-98**
Technical Data and Specifications	**V4-T1-99**
Dimensions	**V4-T1-100**

UL 1053 DIN Rail RCCB 208Y/120 Vac

Product Overview

Optimum product quality, tested reliability and safety stand for best protection of installations and plant. Eaton's UL 1053 Residual Current Circuit Breaker (RCCB) is designed for use in residual current applications.

Application Description

- Motor control circuits
- HVAC internal/external equipment
- PLCs
- HMIs
- Equipment protection

Features

- Wide range of compact RCD type serving as fault-current and additional protection according to UL 1053 and IEC/EN 61008 standards, suitable for worldwide use in the 110V range of applications
- Type A or Type G/A (with delay) protection available
- Comprehensive range of accessories
- Real contact position indicator
- Fault current tripping indicator
- Transparent designation plate
- Trip-free design—RCCB can not be defeated by holding the handle in the ON position
- Captive screws cannot be lost

Standards and Certifications

- UL 1053
- IEC/EN 61008

Listed

Product Selection

UL 1053 RCCB 208Y/120 Vac Type A

Four-Pole

Conditionally Surge Current–Proof 250A, Sensitive to Residual Pulsating DC, Type A

Four-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167699**	FRCmM-25/4/003-A-NA-110
	300	**167702**	FRCmM-25/4/03-A-NA-110
40	30	**167700**	FRCmM-40/4/003-A-NA-110
	300	**167703**	FRCmM-40/4/03-A-NA-110
63	30	**167701**	FRCmM-63/4/003-A-NA-110
	300	**167704**	FRCmM-63/4/03-A-NA-110

UL 1053 RCCB 208Y/120 Vac Type G/A

Type G/A has a 10 ms delay.

Two-Pole

Surge Current–Proof 3 kA, Sensitive to Residual Pulsating DC, Type G/A (ÖVE E 8601)

Two-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167693**	FRCmM-25/2/003-G/A-NA-110
	300	**167696**	FRCmM-25/2/03-G/A-NA-110
40	30	**167694**	FRCmM-40/2/003-G/A-NA-110
	300	**167697**	FRCmM-40/2/03-G/A-NA-110
63	30	**167695**	FRCmM-63/2/003-G/A-NA-110
	300	**167698**	FRCmM-63/2/03-G/A-NA-110

Four-Pole

Surge Current–Proof 3 kA, Sensitive to Residual Pulsating DC, Type G/A (ÖVE E 8601)

Four-Pole

Amperes	GF Sensitivity (mA)	Catalog Number ①	Designation
25	30	**167705**	FRCmM-25/4/003-G/A-NA-110
	300	**167708**	FRCmM-25/4/03-G/A-NA-110
40	30	**167706**	FRCmM-40/4/003-G/A-NA-110
	300	**167709**	FRCmM-40/4/03-G/A-NA-110
63	30	**167707**	FRCmM-63/4/003-G/A-NA-110
	300	**167710**	FRCmM-63/4/03-G/A-NA-110

Note

① Has no thermal element; must be paired with FAZ-NA or FAZ per application.

1

Accessories

UL 1053 DIN Rail RCCB 208Y/120 Vac

	Description	Catalog Number
Contact	Two-pole contact or auxiliary contact / trip indicating contact	**Z-NHK** ①
Padlock Hasp 	Padlock hasp	**Z-IS/SPE-1TE**
Lockoff Device 	UL lockoff device	**FAZPLOFF**

Note

① Voltage of FAZ-NA circuit breaker is limited to 300V with this auxiliary contact installed.

Technical Data and Specifications

- Residual current devices
- Has no thermal protection; must be paired with FAZ-NA or FAZ per application
- Captive screw terminals
- Universal tripping signal switch, also suitable for Z-A; can be mounted subsequently
- Auxiliary switch Z-HK can be mounted subsequently
- Red-green contact position indicator
- White-blue tripping indicator
- Delayed types recommended for use with standard fluorescent tubes with or without electronical ballast (30mA-RCD: 30 units per phase conductor, 100mA-RCD: 90 units per phase conductor)
- The device functions irrespective of the position of installation
- Tripping is line voltage-independent. Consequently, the RCD is suitable for "fault current/residual current protection" and "additional protection" within the meaning of the applicable installation rules
- Reverse-feed permitted
- The four-pole device can also be used for two-pole connection. For this purpose, use terminals 5-6 and N-N
- The test key "T" must be pressed every month. The system operator must be informed of this obligation and responsibility in a way that can be proven (self-adhesive RCD-label enclosed)
- Pressing the test key "T" serves the only purpose of function testing the residual current device (RCD). This test does not make earthing resistance measurement (RE) or proper checking of the earth conductor condition redundant, which must be performed separately
- **Type -A:** Protects against special forms of residual pulsating DC that have not been smoothed
- **Type -G/A:** Additionally protects against special forms of residual pulsating DC that have not been smoothed

UL 1053 DIN Rail RCCB Technical Data

Description	Specification	
Electrical According to IEC/EN 61008		
Design according to	IEC/EN 61008	
	ÖVE E 8601	
Current test marks as printed onto the device		
Tripping Type G	10 ms delay	
Rated voltage U_n	230/400V, 50 Hz	
Rated tripping current $I_{\Delta n}$	30, 300 mA	
Sensitivity	AC and pulsating DC	
Rated insulation voltage U_i	440V	
Rated impulse withstand voltage U_{imp}	4 kV	
Rated short-circuit capacity I_{nc}	10 kA	
Maximum backup fuse	Overload protection	Short-circuit protection
I_n = 25–40A	25A gG/gL	63A gG/gL
I_n = 63A	40A gG/gL	63A gG/gL
Rated breaking capacity I_m bzw. Rated fault breaking capacity $I_{\Delta m}$		
I_n = 25–40A	500A	
I_n = 63A	630A	
Voltage range of test button	Two-pole	100–132V~
	Four-pole	100–230V~
Endurance	Electrical	>4000 operating cycles
	Mechanical	>20,000 operating cycles
Overvoltage category	III	

UL 1053 DIN Rail RCCB Technical Data, continued

Description	Specification	
Electrical According to UL1053		
Design according to	UL 1053	
Current test marks as printed onto the device		
Tripping Type G	8 ms delay	
Rated voltage U_n	208Y/120V, 60 Hz	
Pickup current	22, 200 mA	
Sensitivity	AC and pulsating DC	
Overvoltage tested	530V	
Rated impulse withstand voltage U_{imp}	4 kV	
Rated short-circuit capacity I_{nc}	5 kA according to CSA	
Maximum backup fuse	Overload protection	Short-circuit protection
I_n = 25–40A	25A gG/gL	63A gG/gL
I_n = 63A	40A gG/gL	63A gG/gL
Rated breaking capacity I_m or Rated fault breaking capacity $I_{\Delta m}$		
I_n = 25–40A	500A	
I_n = 63A	630A	
Voltage range of test button	Two-pole	100–121V~
	Four-pole	100–210V~
Endurance	Electrical	>4000 operating cycles
	Mechanical	>20,000 operating cycles
Mechanical		
Frame size	45.0 mm	
Device height	80.0 mm	
Device width	35 mm (2TE), 70 mm (4TE)	
Device width	Quick fastening with two lock-in positions on DIN rail IEC/EN 60715	
Degree of protection, built-in	IP40	
Degree of protection in moisture-proof enclosure	IP54	
Upper and lower terminals	Lift terminals	
Terminal protection	Finger and hand touch safe BGV A3, ÖVE-EN 6	
Terminal capacity	1.5–35 mm^2 single-wire	
	2 x 16 mm^2 multi-wire	
Busbar material thickness	0.8–2 mm	
Tripping temperature	–25°C to +60°C	
Resistance to climatic conditions	According to IEC 61008	
Humidity	5–95%	

Connection Diagram



Two-Pole



Four-Pole

Impact of Ambient Temperature on the Maximum Permanent Current Allowed (A)

Tripping Temperature	16A Two-Pole	16A Four-Pole	25A Two-Pole	25A Four-Pole	40A Two-Pole	40A Four-Pole	63A Two-Pole	63A Four-Pole
40°C	16	16	25	25	40	40	63	63
45°C	14	14	21	22	37	37	59	59
50°C	11	11	18	19	33	34	55	55
55°C	9	9	14	16	30	31	50	50
60°C	①	—	—	—	26	27	45	45

Notes

① Do not use.

Please make sure that these values are not exceeded and that any upstream overload protection switches off in time.

Correct Connection



3+N
(230/400V) IEC
(277/480V) UL



Three-phase load without N
(184–254 Vac Phase-Phase) IEC
(184–277 Vac Phase-Phase) UL



Three-phase load without N
(400 Vac Phase-Phase) IEC
(480 Vac Phase-Phase) UL



1+N
(230V) IEC
(277V) UL

Dimensions

Approximate Dimensions in Inches (mm)

UL 1053 DIN Rail RCCB



Four-Pole

Accessories Technical Data

Description	Z-NHK	Z-IHK-NA
Electrical		
Contact function	2CO	1NO + 1NC
Rated voltage	230V	250V
Frequency	50/60 Hz	50/60 Hz
Rated current	2A	6A
Rated thermal current I_{th}	2A	6A
Utilization category AC13 Rated operational current I_e	3A/250 Vac	3A/250 Vac
Utilization category AC15 Rated operational current I_e	2A/250 Vac	2A/250 Vac
Utilization category DC12 Rated operational current I_e	0.5A/110 Vdc	0.5A/110 Vdc 0.25A/220 Vdc
Rated insulation voltage U_i	250 Vac	250 Vac
Minimum operational voltage per contact U_{min}	5 Vdc	5 Vdc
Minimum operational current I_{min}	10 mA DC	10 mA AC/DC
Rated peak withstand voltage U_{imp} (1.2/50µ)	2.5 kV	4 kV
Conditional short-circuit current I_k with backup fuse 6A	1 kA	1 kA
Maximum backup fuse, overload and short circuit	6A gL	—
Mechanical		
Tripping indicator "electrical tripping"	Blue/white	—
Frame size	45 mm	45 mm
Device height	80 mm	80 mm
Device width	8.8 mm (0.5MU)	8.8 mm (0.5MU)
Mounting	Onto switching device	—
Degree of protection, built-in	IP40	IP40
Terminal protection	Finger and hand touch safe According to BGV A3, ÖVE-EN 6	Finger and hand touch safe According to BGV A3, ÖVE-EN 6
Terminals	Lift terminals	Lift terminals
Terminal capacity	20–14 AWG	0.5–2.5 mm^2
Terminal screws	M3 (Posidrive Z0)	M3 (Posidrive Z0)
Fastening torque of terminal screws	7 lb-in maximum	1.2 Nm

Series G Circuit Breakers

2.1 Introduction

Product Overview V4-T2-2
Typical Applications V4-T2-2
Eaton Molded Case Circuit Breakers in Assemblies V4-T2-3

2.2 Series G®

Globally Accepted Breakers

Product Overview V4-T2-4
Product Selection Overview V4-T2-6
Product Selection Guide V4-T2-7
Technical Data and Specifications V4-T2-9
Dimensions and Weights V4-T2-14
EG-Frame (15–125 Amperes) V4-T2-15
JG-Frame (63–250 Amperes) V4-T2-29
LG-Frame (250–630 Amperes) V4-T2-47
NG-Frame (320–1200 Amperes) V4-T2-65
RG-Frame (800–2500 Amperes) V4-T2-74
Motor Circuit Protectors (MCP) V4-T2-85
Motor Protector Circuit Breakers (MPCB) V4-T2-89
30 mA Ground Fault (Earth Leakage) Module V4-T2-92
Current Limiting Circuit Breaker Module V4-T2-96
High Instantaneous Circuit Breaker for Selective Coordination V4-T2-101
Special Features and Accessories V4-T2-104
Motor Operators V4-T2-112
Plug-In Blocks V4-T2-114
Drawout Cassette V4-T2-115

2.3 Series C®

North American Standards and Special Application Breakers

Product Overview V4-T2-116
Standards and Certifications V4-T2-117
Quick Reference V4-T2-118
G-Frame (15–100 Amperes) V4-T2-121
F-Frame (10–225 Amperes) V4-T2-135
J-Frame (70–250 Amperes) V4-T2-153
K-Frame (70–400 Amperes) V4-T2-161
L-Frame (125–600 Amperes) V4-T2-185
M-Frame (300–800 Amperes) V4-T2-211
N-Frame (400–1200 Amperes) V4-T2-222
R-Frame (800–2500 Amperes) V4-T2-237
Motor Circuit Protectors (MCP) V4-T2-256
Motor Protection Circuit Breakers (MPCB) V4-T2-267
Type ELC Current Limiter Attachment (Size 0–4) V4-T2-269
Current Limiting Circuit Breaker Module V4-T2-270
Internal Accessories V4-T2-273
External Accessories V4-T2-306

2.4 Definite Purpose

Optimized Solution for HVAC/R and Pumping Applications

Definite Purpose Molded Case Circuit Breakers V4-T2-333

2.5 Metering and Communications

Power Monitoring and Metering with Modbus RTU

PM3 Monitoring and Metering Module V4-T2-340

2.6 Specialty

Specialty Breakers

Engine Generator Circuit Breakers V4-T2-343
Direct Current Circuit Breakers V4-T2-349
PVGard™ Solar Circuit Breakers V4-T2-363
E2 Mining Service Breakers V4-T2-372
Classic Mining Breakers V4-T2-398
Add-On Ground Fault Protection—Type GFR V4-T2-412

2.7 Handle Mechanisms

Handle Mechanisms—Series G V4-T2-415
Handle Mechanisms—Series C V4-T2-427

Learn Online

Drawings Online

Series G E-Frame and Series C F-Frame Molded Case Circuit Breakers

Contents

Description	*Page*
Introduction	
Series G	**V4-T2-4**
Series C	**V4-T2-116**
Definite Purpose	**V4-T2-333**
PM3 Monitoring and Metering Module	**V4-T2-340**
Specialty Breakers	**V4-T2-343**

Learn Online Drawings Online

Product Overview

Series G vs. Series C

Eaton's Electrical Sector, under the Eaton brand, offers the widest variety of molded case circuit breakers available today. Designed for electrical and machinery OEMs serving a range of industries and applications, these proven designs incorporate the latest in innovation with the high reliability that has been our hallmark since the advent of the circuit breaker in the 1920s.

The Series C family ranges from 15–2500 amperes, and includes thermal-magnetic breakers, electronic trip breakers, molded case switches, motor circuit protectors, and specially designed breakers for engine generator, DC and mining applications.

The new Series G line features an average 35% size reduction, common field-installable internal accessories, and advanced trip unit functionality that eliminates the need for rating plugs. These breakers meet the requirements of UL®, CSA®, IEC, CCC and CE, allowing the OEM to standardize on a design that meets the needs of their global customer base.

Application Description

Eaton molded case circuit breakers cover the widest range of applications in the industry:

- Electrical OEMs
- Machinery OEMs
- Navy breakers:
  - UL 489 Supplement SB
  - MIL-C-17588
  - MIL-C-17361
  - ABS/NVR
- Mining breakers up to 1100 Vac
- Earth leakage
- DC breakers 125–750 Vdc
- Engine generator breakers 15–1200 amperes
- Current limiting breakers

Typical Applications

Machine Tool Control Panels and Motor Control Centers

Designed for these equipment requirements, including new world-class accessories.

Panelboards

As both main and branch circuit protection devices.

Feeder Pillars

In distribution systems to provide main and branch circuit protection.

Switchgear

In distribution systems to provide main and branch circuit protection up to 2500 amperes (RG-Frame).

Busbar Trunking Tap-Offs

In busbar trunking tap-offs to provide circuit protection.

Individual Enclosures

Completely assembled in enclosures to meet specific customer requirements.

Additional Applications

Special versions of each Eaton frame are available to provide safe equipment control and protection in mining and other applications. Contact your Eaton agent or distributor for additional information.

Typical Eaton Applications



Eaton Molded Case Circuit Breakers in Assemblies

Applications

		Panelboards										Switchboards			Motor Control Centers				
Frame	**Ampere Range**	**1A**	**2A**	**1A-LX**	**2A-LX**	**3A**	**3E**	**4**	**4B**	**4D**	**5P**	**PRL-C**	**PRL-i**	**PRL-C/i**	**Freedom**	***IT.***	**Enclosed Control**	**Bus Plugs**	**Enclosed Breaker**
Series G																			
EG	15–160 ①	—	—	—	—	—	■	—	—	—	—	—	—	—	■	■	■	—	—
JG	20–250	—	—	—	—	—	—	—	—	■	—	—	—	—	—	—	—	—	—
LG	100–630 ②	■	■	—	—	■	■	■	■	■	—	■	—	■	—	—	—	—	■
NG	400–1600	—	—	—	—	—	—	—	■	■	—	■	■	■	■	■	—	—	■
RG	800–2500 ③	—	—	—	—	—	—	—	—	—	—	■	—	■	■	■	—	—	—
Series C																			
FD/ED	15–225	■	■	■	■	■	■	■	■	■	■	■	■	—	■	■	■	■	■
JD	70–250	■	■	—	—	■	—	■	■	■	■	■	■	—	■	■	■	■	■
KD	70–400	■	■	—	—	■	■	■	■	■	■	■	■	■	■	■	■	■	■
LD	400–600	—	—	—	—	■	—	■	■	■	■	■	■	■	■	■	■	■	■
MDL	300–800	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
ND	400–1200	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
RD	800–2500	—	—	—	—	—	—	—	—	—	■	■	-	■	■	■	—	—	—

Notes

① 125 amperes is the maximum UL and CSA rating for EG.
② 600 amperes is the maximum UL and CSA rating for LG.
③ 1200 amperes is the maximum UL and CSA rating for NG.

Series G, 15–2500 Amperes for UL, CSA and IEC Applications

Contents

Description	*Page*
Series G	
Standards and Certifications	**V4-T2-5**
Product Selection Overview	**V4-T2-6**
Product Selection Guide	**V4-T2-7**
Technical Data and Specifications	**V4-T2-9**
Dimensions and Weights	**V4-T2-14**
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Learn Online Drawings Online

Product Overview

Series G, 15–2500 Amperes for UL, CSA and IEC Applications

Eaton Series G molded case circuit breakers provide increased performance in considerably less space than standard circuit breakers or comparable fusible devices.

The "G" signifies global applications: Series G circuit breakers are marked with UL, CSA, CE, IEC and KEMA KEUR listings. Other advantages include:

- Field-fit accessories
- Common accessories through 630 amperes
- Electronic trip units from 20 to 2500 amperes
- UL-listed and IEC-rated, 30 mA ground fault/earth leakage modules
- Built-in ground fault protection down to 20 amperes

The EG, JG and LG frames are designed around space-saving footprints. The NG and RG use the proven Eaton Series C ND and RD designs.

The Series G family includes five frame sizes in ratings from 15 to 2500 amperes. Series G offers a choice of several interrupting capacities up to 200 kA at 480 volts AC (200 kA at 240 volts AC).

Series G molded case circuit breakers are also available in direct current options. Please see Specialty Breakers **Section 2.6** for more details.

Standard calibration is 40 °C. For applications in high ambient temperature conditions, 50 °C factory calibration is available on thermal-magnetic breakers (not UL).

The Most Logically Designed Contact Assembly

The flexibility and outstanding performance characteristics of Eaton circuit breakers are made possible by the best contact designs in circuit breaker history. Our technology creates a high-speed "blow-open" action using the electromechanical forces produced by high-level fault currents.

Eaton circuit breakers are operated by a toggle-type mechanism that is mechanically trip-free from the handle so that the contacts cannot be held closed against short circuit currents. Tripping due to overload or short circuits is clearly indicated by the position on the handle. This remarkably fast and dependable contact action is designed to enhance safety.

Thorough In-Plant Testing

The quality, dependability and reliability of every Eaton Circuit Breaker is ensured by a thorough program of in-plant testing. Two calibration tests are conducted on every pole of every circuit breaker to verify the trip mechanism, operating mechanism, continuity and accuracy.

Current Limiting Characteristics

Circuit breakers are current limiting because of their high repulsion contact arrangement and use of state-of-the-art arc extinguishing technology.

Eaton offers one of the most complete lines of current limiting breakers in the industry. The industrial breakers are available in current limiting versions with interrupting capacities up to 200 kA at 480 V without fuses in the same physical size as standard and high interrupting capacity breakers.

Operating Mechanisms

Eaton circuit breakers have a toggle handle operating mechanism, which also serves as a switching position indicator. The indicator shows the positions of: ON, OFF and TRIPPED.

The toggle handle snaps into the TRIPPED position if the breaker is tripped by one of its overcurrent, short circuit, shunt or undervoltage releases. Before the circuit breaker can be reclosed following a trip-out, the toggle handle must be brought beyond the OFF position (RESET). The circuit breaker can then be reclosed.

As an additional switching position indicator for EG- to RG-Frame circuit breakers, there are two windows on the right and on the left of the toggle handle, in which the switching state is indicated by means of the colors red, green and white corresponding to the ON, OFF and TRIPPED positions respectively.

Positions of the Toggle Handle Drive



Standards and Certifications

Eaton Series G circuit breakers meet applicable UL 489 and IEC 60947-2 standards.

Molded case circuit breakers from Eaton are designed to conform with the following international standards:

- Australian Standard AS 2184 and AS 3947-2 molded case circuit breakers
- British Standards Institution Standard EN60947.2
- International Electromechanical Commission Recommendations IEC 60947.2 circuit breakers

CE

- Japanese T-Mark standard molded case circuit breakers
- National Electrical Manufacturers Association Standards Publication No. AB1-1993 molded case circuit breakers
- South African Bureau of Standards, Standard SANS 156, Standard Specification for molded case circuit breakers
- Swiss Electro-Technical Association Standard SEV 947.2, Safety Regulations for circuit breakers
- Union Technique de l'Electricite Standard NF C 63-120, low voltage switchgear and control gear circuit breaker requirements
- Verband Deutscher Elektrotechnike (Association of German Electrical Engineers) Standard VDE 0660, low voltage switchgear and control gear, circuit breakers

Global Third-Party Certification

Certification marks ensure product compliance with the total standard via the third party witnessing of tests by globally recognized independent certification organizations.

KEMA is a highly recognized, independent international organization that offers certification and inspection facilities for equipment in many industries. The KEMA-KEUR mark is the highest certification an electrical product can receive from KEMA. Our IEC 60947-2 molded case circuit breakers are KEMA tested and certified. These breakers are also listed in accordance with UL 489, as well as CSA C22.2 No. 5-02.

KEMA, UL and CSA provide ongoing follow-up testing and inspections to ensure that Eaton molded case circuit breakers continue to meet their exacting standards.

ISO Certification

Eaton circuit breakers are manufactured in ISO® certified facilities.

Product Selection Overview

Electronic Trip Units (Digitrip RMS Trip Units)—Multi-Function Electronic Trip Units for All Applications

True rms Sensing

Digitrip RMS trip units use Eaton's microprocessor-based intelligence to provide true rms sensing, permitting increased accuracy and reliable system protection. True rms sensing is not susceptible to nuisance tripping when waveforms containing high harmonic currents are present.

Digitrip RMS 310+

Digitrip RMS 310+ electronic trip units are available with Eaton Series G circuit breakers JG, LG, NG and RG, as well as Series C FD, KD, LD and MDL circuit breakers.

Digitrip 310+ trip units are equipped with an integrated I_r switch that allows users to modify the continuous current rating of the breaker without having to replace a rating plug. This provides further flexibility for coordination in systems. The trip units may be used in 50 Hz or 60 Hz applications. The Digitrip 310+ offers true rms sensing, is front adjustable and has an optional local display of current and cause of trip.

Curve Shaping

When selectively coordinated systems are called for, Digitrip RMS 310+ will provide a cost-effective solution for a variety of applications.

The standard Digitrip RMS 310+ includes an adjustable short time pickup setting encompassing an I^2t ramp function that provides the basic LS curve shaping function.

Digitrip 310+ trip units also include selectable long time delay (t_{LD}) and pickup settings (I_r). A rating plug is not required.

The optional Digitrip RMS 310+ LSI and LSIG provide additional flat response short time delay adjustments and an instantaneous setting to provide LSI curve shaping capability.

Digitrip RMS 310+ LSG and LSIG units are available with ground fault pickup and flat response ground fault delay. Ground fault alarm options are available with trip and no trip functionality as a means to notify users of a ground fault condition with the option to maintain the breaker online.

Digitrip RMS 310+ trip units can effectively coordinate with both sophisticated upstream power breakers as well as downstream thermal-magnetic breakers, making Digitrip RMS 310+ trip units the cost-effective reliable choice for selectively coordinated systems.

Thermal Memory

All Digitrip RMS trip units incorporate a long delay. Thermal memory prevents the system from cumulative overheating due to repeated overcurrent events that may occur in quick succession.

Field Testing

A field test kit is available for Digitrip RMS 310+ trip units.

Arcflash Reduction Maintenance Mode (ARMS)

ARMS is an available feature on KD, LG, LD, MDL, NG and RG frames with 310+ electronic trip units. This feature increases worker safety by providing an accelerated instantaneous trip unit to reduce arc flash. Additionally, LG, NG and RG frames with the ARMS feature include a fully adjustable instantaneous setting.

Digitrip RMS 610 and 910

Digitrip RMS 610 and 910 trip units are available with Eaton R-Frame circuit breakers 800 through 2500 amperes. Digitrip 610 and 910 trip units provide unparalleled system protection with the added convenience of a local display.

Curve Shaping

Digitrip RMS 610 and 910 trip units are available with up to nine curve shaping choices achieved by adjusting up to seven switches on the front of the unit for optimum system coordination. Maximum curve shaping flexibility is provided by dependent long and short delay adjustments that are long delay pickup (I_r) based, depicted on the front of the unit by the blue portion of the time-current curve.

Additional coordination capability can be provided by utilizing the short delay and ground fault zone selective interlocking features available on these trip units.

System Diagnostics

Digitrip RMS 610 and 910 models of trip units provide long delay, short delay, instantaneous, and ground fault cause of trip LEDs on the front of the unit. Their display shows a magnitude of trip information, as well as remote signal contacts, for improved system alarming.

System Monitoring

Digitrip 610 and 910 trip units have the capability to monitor phase currents, as well as neutral or ground currents. This information is displayed on a large digital display mounted on the unit.

Digitrip RMS 910 trip units can also provide the user with power and energy monitoring capability. Peak power demand, present power demand, and total energy, as well as forward and reverse energy can be monitored with this unit.

Digitrip RMS 910 trip units have the additional capability of monitoring line-to-line voltage, as well as system power factor. Both parameters are displayed in the digital display window and are supported by LEDs to indicate which parameter is being displayed.

Harmonics Monitoring

Digitrip RMS 910 trip units are capable of displaying values of current harmonics in the digital display window. Percentage of harmonic content can be monitored for each phase, up to the 27th harmonic. Additionally, a total harmonic distortion value can be calculated and displayed.

Communications

Digitrip RMS 910 units have built-in communications options to allow all protection, monitoring, and control information to be transmitted back to a central location via the Eaton PowerNet™ system.

Field Testing

Integral field testing capability is provided on all 610 and 910 trip units. No additional test set is needed to perform both trip and no trip field testing.

Product Selection Guide

Electronic Trip Units

Digitrip—RMS 310+, 610 and 910

RMS 310+

RMS 610

RMS 910

Breaker Type					
Series G frame(s)		JG-, LG-, NG- and RG-Frames		RG-Frame	RG-Frame
Ampere rating		20–2500 A		800–2500 A	800–2500 A
Interrupting rating at 415 V		35, 70, 100 kA		70, 100 kA	70, 100 kA
Trip Unit Sensing					
rms sensing		Yes		Yes	Yes
Protection and Coordination					
Protection	Ordering options	LS, LSG	LSI, LSIG	LI, LS, LSI, LIG, LSG, LSIG	LI, LS, LSI, LIG, LSG, LSIG
	Fixed rating plug (I_n) ①	Yes	Yes	Yes	Yes
	Overtemperature trip	Yes	Yes	Yes	Yes
Long delay	Adjustable I_r switch	Yes	Yes	No	No
	Long delay setting	VAR/frame	VAR/frame	0.5–1.0 x (I_n)	0.5–1.0 x (I_n)
	Long delay time I^2t at 6x	10 seconds ②	10 seconds ②	2–24 seconds	2–24 seconds
	Long delay thermal memory	Yes	Yes	Yes	Yes
	High load alarm	1.05 I_r	1.05 I_r	0.85 x I_r	0.85 x I_r
Short delay	Short delay setting	VAR/frame ④	VAR/frame ④	200–600% S1 and S2 x (I_r)	200–600% S1 and S2 x (I_r)
	Short delay time I^2t	100 ms	No	100, 300, 500 ms	100, 300, 500 ms
	Short delay time flat	No	I–300 ms	100–500 ms	100–500 ms
	Short delay time ZSI	No	Yes	Yes	Yes
Instantaneous	Independent adjustable Inst. setting	No	Yes ⑤	Yes	Yes
	Instantaneous setting	No	VAR/frame	200–600% M1 and M2 x (I_n)	200–600% M1 and M2 x (I_n)
	Discriminator	No	No	Yes ⑥	Yes ⑥
	Instantaneous override	Yes	Yes	Yes	Yes
Ground fault	Ground fault setting	VAR/Frame ⑦	VAR/Frame ⑦	25–100% x (I_n) ⑦	25–100% x (I_n) ⑦
	Ground fault delay I^2t at 0.62x	No	No	100, 300, 500 ms	100, 300, 500 ms
	Ground fault delay flat	I–300 ms	I–300 ms	100–500 ms	100–500 ms
	Ground fault ZSI	No	Yes	Yes	Yes
	Ground fault thermal memory	No	No	Yes	Yes

Notes

I_n = Rating plug rating.
I_r = Long delay setting.

① 310+ trip units have selectable settings instead of a rating plug.
② 310+ trip units have adjustable long delay times of 2–24 seconds, except NG 310+ for 800 A frame, for which it is 2–14 seconds.
③ 310+ details are included by frame in **Pages V4-T2-44** (JG), **V4-T2-62** (LG), **V4-T2-72** (NG), and **V4-T2-83** (RG).
④ JG/LG: 2X–14X (I_n); NG: 2X–8X (I_n); RG: 2X–9X (I_n); 2500 ampere RG-Frame 2X–6X% x (I_n).
⑤ LG, NG and RG ALSI and ALSIG 310+ trip units include an independently adjustable Instantaneous (I_i) setting.
⑥ LS, LSG only.
⑦ Not to exceed 1200 amperes.

Digitrip—RMS 310+, 610 and 910, continued

RMS 310+

RG

JG

LG/NG

RMS 610

RMS 910

	LS, LSG	LSI, LSIG	LSI, LSIG, LSIG (A)	LSI (A), LSIG
System Diagnostics				
Cause of trip LEDs	Yes ①②	Yes ①②	Yes	Yes
Magnitude of trip information	No	No	Yes	Yes
Remote signal contacts	No	No	Yes	Yes
System Monitoring				
Digital display	Yes ③	Yes ③	Yes	Yes
Current	Yes ③	Yes ③	Yes	Yes
Voltage	No	No	No	Yes
Power and energy	No	No	No	Yes
Power quality—harmonics	No	No	No	Yes
Power factor	No	No	No	Yes
System Communications				
PowerNet	No	No	No	Yes
Field Testing				
Testing method	Test set ④	Test set ④	Integral	Integral

Notes

① Using cause of trip module (catalog number **TRIP-LED**).
② RG 310+ trip units include integrated cause of trip LEDs.
③ Using ammeter or remote ammeter/cause of trip display (catalog number **DIGIVIEW** and **DIGIVIEWR06**).
④ Test kit available for field testing 310+ trip units (catalog number **MTST230V**).

Technical Data and Specifications

Ratings

Frames EG, JG and LG

EG

JG

LG

Maximum rated current (amperes)			125, 160 ①								250						400, 630 ②					
Breaker type ③			B	B	E	S	S	H	H	C	E	S	H	C	U	X	E	S	H	C	U	X
Number of poles			1	2, 3, 4	2, 3, 4	1	2, 3, 4	1	2, 3, 4	3, 4	2, 3, 4	2, 3, 4	2, 3, 4	3, 4	3, 4	3, 4	3, 4	3, 4	3, 4	3, 4	3, 4	3, 4
Breaker Capacity (kA rms) Vac 50–60 Hz																						
NEMA®, UL, CSA	240 Vac		25	25	35	85	85	100	100	200	65	85	100	200	200	200	65	85	100	200	200	200
	480 Vac		—	18	25	—	35	—	65	100	25	35	65	100	150	200	35	50	65	100	150	200
	600 Vac ④		—	—	18	—	22	—	25	35	18	18	25	35	50	50	18	25	35	50	65	65
	125/250 Vdc ⑤		10 ⑥	10	10	35 ⑥	35	42 ⑥	42	42	10	22	22	42	50	50	22	22	42	42	50	50
IEC 60947-2	220–240 Vac	I_{cu}	25	25	35	85	85	100	100	200	65	85	100	200	200	200	65	85	100	200	200	200
		I_{cs}	25	25	35	43	43	50	50	200	65	85	100	200	200	200	65	85	100	200	200	200
	380–415 Vac	I_{cu}	—	18	25	—	40	—	70	100	25	40	70	100	150	200	35	50	70	100	150	200
		I_{cs}	—	18	25	—	30	—	35	100	25	40	70	100	150	200	35	50	53	100	150	200
	660–690 Vac	I_{cu}	—	—	—	—	—	—	—	—	12	12	14	16	18	18	12	20	25	30	35	35
		I_{cs}	—	—	—	—	—	—	—	—	6	6	7	12	14	14	6	10	13	15	18	18
	125/250 Vdc ⑤	I_{cu}	10 ⑥	10	10	35 ⑥	35	42 ⑥	42	42	10	22	22	42	50	50	22	22	42	42	50	50
		I_{cs}	10 ⑥	10	10	35 ⑥	35	42 ⑥	42	42	10	22	22	42	50	50	22	22	42	42	50	50
Ampere range			15–160 A ①								20–250 A						100–630 A ②					
Trip Units F = Fixed A = Adjustable T = Thermal M = Magnetic			FT-FM AT-FM								FT-AM AT-AM Electronic (Digitrip RMS 310)						FT-AM AT-AM Electronic (Digitrip RMS 310)					
	Interchangeable		—	—	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
	Built-in		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Thermal magnetic	Fixed thermal		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Adjustable thermal		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Magnetic		Fixed								Adjustable						Adjustable					
Electronic RMS ⑦	LS		—	—	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
	LSI		—	—	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
	LSG		—	—	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
	LSIG		—	—	—	—	—	—	—	—	■	■	■	■	■	■	■	■	■	■	■	■
	ALSI		—	—	—	—	—	—	—	—	—	—	—	—	—	—	■	■	■	■	■	■
	ALSIG		—	—	—	—	—	—	—	—	—	—	—	—	—	—	■	■	■	■	■	■
Utilization category			A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A

Notes

① 125 amperes is the maximum UL and CSA rating for the EG.
② 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA listed rating for the LG.
③ Breaker type C, U and X are current limiting per UL 489.
④ EG breaker rated 600/347 Vac.
⑤ Two poles in series.
⑥ 125 Vdc only for single-pole breakers.
⑦ Not suitable for DC application. Four-pole ground fault not available.

Frames NG and RG

NG

RG

Maximum rated current (amperes)			800, 1200	800, 1200	800, 1200	1600 ①	800	1600, 2000, 2500	1600, 2000, 2500
Breaker type			S	H	C ②	S	U	H	C ②
Number of poles			2, 3, 4	2, 3, 4	2, 3, 4	3	3	3, 4	3, 4
Breaker Capacity (kA rms) AC 50–60 Hz									
NEMA, UL, CSA	240 Vac		85	100	200	—	200	125	200
	480 Vac		50	65	100	—	150	65	100
	600 Vac		25	35	65	—	65	50	65
IEC 60947-2	220–240 Vac	I_{cu}	85	100	200	85	—	135	200
		I_{cs}	85	100	100	85	—	100	100
	380–415 Vac	I_{cu}	50	70	100	50	—	70	100
		I_{cs}	50	50	50	50	—	50	50
	660–690 Vac	I_{cu}	20 ③	25 ③	35	20 ③	—	25 ③	35 ③
		I_{cs}	10	13	18	10	—	13	18
	250 Vdc	I_{cu}	—	—	—	—	—	—	—
		I_{cs}	—	—	—	—	—	—	—
Ampere range			400–1200 A	400–1200 A	400–1200 A	1600 A	800 A	800–2500 A	800–2500 A
Trip units			Electronic (Digitrip RMS 310+)					Electronic (Digitrip RMS 310+ and 910)	
	Interchangeable		—	—	—	—	—	■ ⑤	■ ⑤
	Built-in		■	■	■	■	■	■	■
Electronic ④	LI		—	—	—	—	—	■ ⑥	■ ⑥
	LS		■	■	■	■	■	■	■
	LSI		■	■	■	■	■	■	■
	LIG		—	—	—	—	—	■ ⑥	■ ⑥
	LSG		■	■	■	■	■	■	■
	LSIG		■	■	■	■	■	■	■
	ALSI		■	■	■	■	—	■	■
	ALSIG		■	■	■	■	—	■	■
Utilization category			A	A	A	A	A	A	A

Notes

① NG 1600 ampere frame is not UL or CSA listed.
② Not KEMA-KEUR listed.
③ IEC 60947-2 H.5 Annex H is not KEMA-KEUR tested.
④ Not suitable for DC application. Four-pole ground fault not available.
⑤ RG 310+ are interchangeable with the exception of: FROM not ground fault equipped TO ground fault equipped
⑥ Available only on Digitrip 910 trip units.

General Specifications

All Series G Frames

	EG	JG	LG	NG	RG
Maximum rated current I_n depending on the version	160 A ①	250 A	400, 630 A ②	800, 1200, 1600 A ③	1600, 2000, 2500 A
Rated insulation voltage U, according to IEC 60947-2					
Main conducting paths	500 Vac	750 Vac	750 Vac	750 Vac	750 Vac
Auxiliary circuits	500 Vac	690 Vac	690 Vac	690 Vac	690 Vac
Rated impulse withstand voltage U_{imp}					
Main conducting paths	6 kV	8 kV	8 kV	8 kV	8 kV
Auxiliary circuits	4 kV	4 kV	4 kV	4 kV	4 kV
Rated operational voltage U_e					
IEC	415 Vac	690 Vac	690 Vac	690 Vac	690 Vac
NEMA	600Y/347 Vac	600 Vac	600 Vac	600 Vac	600 Vac
UL and CSA listed	Yes ①	Yes	Yes ②	Yes ③	Yes
Permissible ambient temperature	–20 ° to 70 °C	–20 ° to 70 °C	–20 ° to 70 °C	–20 ° to 70 °C	–20 ° to 70 °C
Permissible load for various ambient temperatures close to the circuit breaker, related to the rated current of the circuit breaker	④ ⑤	④ ⑤	④ ⑤	—	—
Circuit breakers for plant protection					
At 40 °C	100% 100%	100% 100%	100% 100%	100%	100%
At 50 °C	96% 92%	96% 94%	96% 91%	91%	91%
At 55 °C	93% 87%	94% 90%	93% 86%	85%	85%
At 60 °C	91% 83%	92% 87%	90% 82%	81%	81%
At 70 °C	86% 73%	88% 80%	84% 70%	70%	70%
Circuit breakers for motor protection					
At 40 °C	—	100%	100%	—	—
At 50 °C	—	100%	100%	—	—
At 55 °C	—	100%	100%	—	—
At 60 °C	—	100%	100%	—	—
At 70 °C	—	90%	90%	—	—
Circuit breakers for starter combinations and isolating circuit breakers					
At 40 °C	100%	100%	100%	100%	100%
At 50 °C	100%	100%	100%	91%	91%
At 55 °C	96%	96%	95%	85%	85%
At 60 °C	91%	82%	90%	81%	81%
At 70 °C	86%	88%	84%	—	—
Rated short-circuit breaking capacity (DC) Not for circuit breakers for motor protection (Time constant t = 10 rms)					
Two conducting paths in series For EG to LG up to 250 Vdc	42 kA max.	42 kA max.	42 kA max.	⑥	⑥
NEMA (time constant t = 8 rms) Two conducting paths in series 250 Vdc	42 kA max.	42 kA max.	42 kA max.	⑥	⑥

Notes

① 125 amperes is the maximum UL and CSA rating for the EG.
② 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA rating for the LG.
③ 1200 amperes is the maximum UL and CSA rating for the NG.
④ Thermal overload release set to the lower value.
⑤ Thermal overload release set to the upper value.
⑥ Not suitable for DC switching.

All Series G Frames, continued

	EG	JG	LG		NG	RG
Main switch characteristics according to IEC 60947-2 in combination with lockable rotary drives	Yes	Yes	Yes		Yes	Yes
Rated short circuit breaking capacity according to IEC 60947-2 (at AC 50/60 Hz)	For rated short circuit breaking capacity, see **Page V4-T2-9**.					
Endurance (operating cycles)	10,000	10,000	8,000		3,000	3,000
Maximum switching frequency	300 1/h	240 1/h	240 1/h		60 1/h	60 1/h
Conductor cross sections and terminal types for main conductors	Box terminals	Box terminals	Box terminals	Flat bar terminals	Flat bar terminals	Flat bar terminals
Solid or stranded	2.5 to 95 mm^2	50 to 150 mm^2	95 to 240 mm^2	—	—	—
Finely stranded with end sleeve	2.5 to 50/70 mm^2	35 to 120 mm^2	70 to 150 mm^2	—	—	—
Busbar	—	—	—	600 A	Optional	Optional
Tightening torque for box terminals	5.6 Nm	20 Nm	42 Nm	31 Nm	31 Nm	—
Tightening torque for busbar connection pieces	5.6 Nm	15 Nm	30 Nm	6 Nm	50 Nm	20 Nm
Conductor cross sections for auxiliary circuits with terminal connection or terminal strip						
Solid	0.75 to 2.5 mm^2	0.75 to 2.5 mm^2	0.75 to 2.5 mm^2		Up to 2x4 mm^2	Up to 2x4 mm^2
Finely stranded with end sleeve	0.75 to 2.5 mm^2	0.75 to 2.5 mm^2	0.75 to 2.5 mm^2		Up to 2x2.5 mm^2	Up to 2x2.5 mm^2
With brought-out cable ends	—	0.82 (AWG 18) mm^2	0.82 (AWG 18) mm^2		0.82 (AWG 18) mm^2	0.82 (AWG 18) mm^2
Tightening torque for fitting screws	—	0.8 to 1.4 Nm	0.8 to 1.4 Nm		0.8 to 1.4 Nm	0.8 to 1.4 Nm
Power loss per circuit breaker at maximum rated current I_n (the power losses of the undervoltage releases ("r" releases) must be observed if necessary) at three-phase symmetrical load)			400 A:	600 A:		
For plant protection	40 W	45 W	65 W	120 W	87/210 W	220/270/400 W
As isolating circuit breaker	40 W	45 W	65 W	120 W	87/210 W	220/270/400 W
For starter combinations	40 W	45 W	65 W	120 W	—	—
For motor protection	—	45 W	65 W	120 W	—	—
Permissible mounting position						
Arc spacing— suitable for reverse-feed applications	Yes (except HMCPE)	Yes	Yes		Yes	Yes
Auxiliary Switches						
Rated thermal current I_{th}	6A	6A	6A		6A	6A
Rated making capacity	20 A	20 A	20 A		20 A	20 A
	AC-14	**AC-14**	**AC-14**		**AC-15**	**AC-15**
Rated operational voltage	230/400/600 V	230/400/600 V	230/400/600 V		600 V	600 V
Rated operational current	6/3/0.25 A	6/3/0.25 A	6/3/0.25 A		6A	6A
					DC-13	**DC-13**
Rated operational voltage	125/250V	125/250V	125/250V		125/250V	125/250V
Rated operational current	0.5/0.15 A	0.5/0.15 A	0.5/0.15 A		0.5/0.25 A	0.5/0.25 A
Backup fuse	6/4/4 A	(4) 6/4/4 A	(4) 6/4/4 A		(4) 6/4/4 A	(4) 6/4/4 A
Miniature circuit breaker	6/4 A	6/4 A	6/4 A		6/4 A	6/4 A

All Series G Frames, continued

	EG	JG	LG	NG	RG
Releases					
Undervoltage releases ("r" releases)					
Response voltage:					
Drop (breaker tripped) U_s	35–70%	35–70%	35–70%	35–70%	35–70%
Pickup (breaker may be switched on) U_s	85–110%	85–110%	85–110%	85–110%	85–110%
Power consumption in continuous operation at:					
50/60 Hz 12 Vac	—	—	—	1.9 VA	2.9 VA
50/60 Hz 24 Vac	0.72 VA	3.9 VA	3.9 VA	2.4 VA	3.1 VA
50/60 Hz 48–60 Vac	1.15–1.78 VA	2.5–3.8 VA	2.5–3.8 VA	2.3–4.1 VA	3.4–6.0 VA
50/60 Hz 110–127 Vac	0.96–1.25 VA	1.8–2.4 VA	1.8–2.4 VA	3.4–4.2 VA	3.3–3.8 VA
50/60 Hz 208–240 Vac	1.28–1.68 VA	2.7–3.8 VA	2.7–3.8 VA	4.8–6.5 VA	4.2–7.2 VA
50/60 Hz 380–500 Vac	2.2–3.9 VA	3.4–5.8 VA	3.4–5.8 VA	6.8–12.0 VA	3.8–10.0 VA
50/60 Hz 525–600 Vac	3.4–4.3 VA	3.4–4.3 VA	3.4–4.3 VA	—	—
12 Vdc	—	—	—	2.6W	3.4W
24 Vdc	0.70 W	3.1W	3.1W	3.6W	4.3W
48–60 Vdc	1.12–1.76W	2.0–3.1W	2.0–3.1W	3.5–5.5W	4.8–7.2W
110–125 Vdc	0.94–1.21W	1.6–2.2W	1.6–2.2W	2.9–3.6W	3.3–3.8W
220–250 Vdc	1.45–1.86W	3.1–4W	3.1–4W	4.8–6.3W	6.6–7.5W
Maximum opening time	50 ms	50 ms	50 ms	62 ms	62 ms
Shunt Trips					
Shunt trips ("f" releases)					
Response voltage:					
Pickup (breaker tripped) U_s	70–110%	70–110%	70–110%	70–110%	70–110%
Power consumption in (short time) at:					
50/60 Hz 24 Vac	10–41 VA	87–405 VA	87–405 VA	98–475 VA	612 VA
50/60 Hz 48–60 Vac	139–210 VA	710–1105 VA	710–1105 VA	24–50 VA	403–666 VA
50/60 Hz 48–127 Vac	—	—	—	—	—
50/60 Hz 110–240 Vac	83–360 VA	66–432 VA	66–432 VA	67–432 VA	396–1896 VA
50/60 Hz 380–440 Vac	—	127–188 VA	127–188 VA	76–110 VA	1596–2156 VA
50/60 Hz 380–600 Vac	418–1080 VA	—	—	—	—
50/60 Hz 480–600 Vac	—	34–60 VA	34–60 VA	19–42 VA	230–384 VA
12–24 Vdc	29–120 W	164–631 W	164–631 W	145–610 W	396 W
48–60 Vdc	475–720 W	830–1580 W	830–1580 W	67–102 W	341–528 W
110–125 Vdc	99–121 W	112–150 W	112–150 W	121–150 W	264–350 W
220–250 Vdc	—	40–58W	40–58 W	46–55 W	374–475 W
Maximum load duration	Interrupts automatically	Interrupts automatically	Interrupts automatically	Interrupts automatically	Interrupts automatically
Maximum opening time	50 ms	50 ms	50 ms	62 ms	62 ms
Molded Case Switch (with High Magnetic Trip)					
Unfused kAIC at 480 Vac (415 Vac)	65 (70)	65 (70)	65 (70)	65 (70)	65 (70)
Self-protected, will trip above 	1250 for EG125; 1600 for EG160	2500	4000/6300	12,500	20,000

Dimensions and Weights

Approximate Dimensions in Inches (mm)

Series G—Frame EG, JG and LG

	EG			JG			LG		
	H	W	D	H	W	D	H	W	D
Single-pole	5.50 (139.7)	1.00 (25.4)	2.99 (76.0)	—	—	—	—	—	—
Two-pole	5.50 (139.7)	2.00 (50.8)	2.99 (76.0)	7.00 (177.8)	4.13 (105.0)	3.57 (87.4)	—	—	—
Three-pole	5.50 (139.7)	3.00 (76.2)	2.99 (76.0)	7.00 (177.8)	4.13 (105.0)	3.57 (87.4)	10.13 (258.0)	5.48 (140.0)	4.09 (104.0)
Four-pole	5.50 (139.7)	4.00 (101.6)	2.99 (76.0)	7.00 (177.8)	5.34 (135.6)	3.57 (87.4)	10.13 (258.0)	7.22 (183.0)	4.09 (104.0)

Series G—Frame NG and RG

	NG			RG		
	H	W	D	H	W	D
Single-pole	—	—	—	—	—	—
Two-pole	—	—	—	—	—	—
Three-pole	16.00 (406.0)	8.25 (210.0)	5.50 (140.0)	16.00 (406.0)	15.50 (394.0)	9.75 (229.0)
Four-pole	16.00 (406.0)	11.13 (280.0)	5.50 (140.0)	16.00 (406.0)	20.00 (508.0)	9.75 (229.0)

Approximate Shipping Weight in Lbs (kg)

Series G—Frame EG, JG and LG

	EG	JG	LG	NG	RG
Single-pole	0.85 (0.39)	—	—	—	—
Two-pole	1.57 (0.71)	11.3 (5.13)	—	—	—
Three-pole	2.28 (1.04)	5.06 (2.30) T/M 5.31 (2.41) ETU	12.36 (5.61) T/M 13.04 (5.92) ETU	46.8 (21.3)	103.0 (47.0)
Four-pole	2.85 (1.29)	6.76 (3.07) T/M 7.12 (3.23) ETU	16.27 (7.39) T/M 16.92 (7.68) ETU	62.0 (28.3)	118.4 (54.0)

EG-Frame (15–125 Amperes)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	
Catalog Number Selection	**V4-T2-16**
Product Selection	**V4-T2-17**
Accessories	**V4-T2-26**
Technical Data and Specifications	**V4-T2-27**
Dimensions and Weights	**V4-T2-27**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

EG-Frame (15–125 Amperes)

Product Description

EG breaker is HACR rated.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

2

Series G—EG-Frame (15–125 Amperes)



Frame
E

Standard/Application
G = IEC/CE/UL/CSA

Performance				
	600Y/347	**480**	**415**	**240**
B	—	18	18	25
E	18	25	25	35
S	22	35	40	85
H	25	65	70	100
C	35	100	100	200
K	Molded case switch ②			

Number of Poles
1 = One
2 = Two
3 = Three
4 = Four—neutral 0% protected
7 = Four—neutral 100% protected

Amperes
016 ①
015
020
025
030
032 ①
035
040
045
050
060
063 ①
070
080
090
100
110
125
160 ①

Terminations/Hardware	
Terminals	**Mounting Hardware**
M = Metric end caps	Metric
E = Imperial end caps	Imperial
G = Line/load standard	Metric
B = Bolt-on	—

Trip Unit
FF = Fixed fixed
AF = Adjustable thermal fixed magnetic
KS = Molded case switch

Notes

① Cannot be UL rated.

② Available only as 125 and 160 A sizes.

Product Selection

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware) IC Rating at 415/480 Volts

EG-Frame

EG-Frame—18/18

Maximum Continuous Amps at 40 °C ①	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Adjustable ② Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Fixed Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Adjustable ② Thermal, Fixed Magnetic Catalog Number
15	EGB1015FFG	EGB2015FFG	EGB3015FFG	—	EGB4015FFG	—
16	EGB1016FFG	EGB2016FFG	EGB3016FFG	—	EGB4016FFG	—
20	EGB1020FFG	EGB2020FFG	EGB3020FFG	—	EGB4020FFG	EGB4020AFG
25	EGB1025FFG	EGB2025FFG	EGB3025FFG	EGB3025AFG	EGB4025FFG	EGB4025AFG
30	EGB1030FFG	EGB2030FFG	EGB3030FFG	—	EGB4030FFG	—
32	EGB1032FFG	EGB2032FFG	EGB3032FFG	EGB3032AFG	EGB4032FFG	EGB4032AFG
35	EGB1035FFG	EGB2035FFG	EGB3035FFG	—	EGB4035FFG	—
40	EGB1040FFG	EGB2040FFG	EGB3040FFG	EGB3040AFG	EGB4040FFG	EGB4040AFG
45	EGB1045FFG	EGB2045FFG	EGB3045FFG	—	EGB4045FFG	—
50	EGB1050FFG	EGB2050FFG	EGB3050FFG	EGB3050AFG	EGB4050FFG	EGB4050AFG
60	EGB1060FFG	EGB2060FFG	EGB3060FFG	—	EGB4060FFG	—
63	EGB1063FFG	EGB2063FFG	EGB3063FFG	EGB3063AFG	EGB4063FFG	EGB4063AFG
70	EGB1070FFG	EGB2070FFG	EGB3070FFG	—	EGB4070FFG	—
80	EGB1080FFG	EGB2080FFG	EGB3080FFG	EGB3080AFG	EGB4080FFG	EGB4080AFG
90	EGB1090FFG	EGB2090FFG	EGB3090FFG	—	EGB4090FFG	—
100	EGB1100FFG	EGB2100FFG	EGB3100FFG	EGB3100AFG	EGB4100FFG	EGB4100AFG
110	EGB1110FFG	EGB2110FFG	EGB3110FFG	—	EGB4110FFG	—
125	EGB1125FFG	EGB2125FFG	EGB3125FFG	EGB3125AFG	EGB4125FFG	EGB4125AFG
160	—	—	EGB3160FFG	EGB3160AFG	EGB4160FFG	EGB4160AFG

Notes

① 16, 32, 63 and 160 A are not UL listed ratings.
② Adjustable thermal are not UL listed.
③ Change the fourth digit to 7 for 100% neutral protection. Neutral is on the LH side.

EG-Frame—25/25 Single-Pole Unavailable

EG-Frame

EG-Frame—25/25

Maximum Continuous Amps at 40 °C ①	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Adjustable ② Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Fixed Thermal, Fixed Magnetic Catalog Number	Four-Pole Adjustable ② Thermal, Fixed Magnetic Catalog Number
15	**EGE2015FFG**	**EGE3015FFG**	—	**EGE4015FFG**	—
16	**EGE2016FFG**	**EGE3016FFG**	—	**EGE4016FFG**	—
20	**EGE2020FFG**	**EGE3020FFG**	—	**EGE4020FFG**	**EGE4020AFG**
25	**EGE2025FFG**	**EGE3025FFG**	**EGE3025AFG**	**EGE4025FFG**	**EGE4025AFG**
30	**EGE2030FFG**	**EGE3030FFG**	—	**EGE4030FFG**	—
32	**EGE2032FFG**	**EGE3032FFG**	**EGE3032AFG**	**EGE4032FFG**	**EGE4032AFG**
35	**EGE2035FFG**	**EGE3035FFG**	—	**EGE4035FFG**	—
40	**EGE2040FFG**	**EGE3040FFG**	**EGE3040AFG**	**EGE4040FFG**	**EGE4040AFG**
45	**EGE2045FFG**	**EGE3045FFG**	**EGE3050AFG**	**EGE4045FFG**	—
50	**EGE2050FFG**	**EGE3050FFG**	—	**EGE4050FFG**	**EGE4050AFG**
60	**EGE2060FFG**	**EGE3060FFG**	—	**EGE4060FFG**	—
63	**EGE2063FFG**	**EGE3063FFG**	**EGE3063AFG**	**EGE4063FFG**	**EGE4063AFG**
70	**EGE2070FFG**	**EGE3070FFG**	—	**EGE4070FFG**	—
80	**EGE2080FFG**	**EGE3080FFG**	**EGE3080AFG**	**EGE4080FFG**	**EGE4080AFG**
90	**EGE2090FFG**	**EGE3090FFG**	—	**EGE4090FFG**	—
100	**EGE2100FFG**	**EGE3100FFG**	**EGE3100AFG**	**EGE4100FFG**	**EGE4100AFG**
125	**EGE2125FFG**	**EGE3125FFG**	**EGE3125AFG**	**EGE4125FFG**	**EGE4125AFG**
160	—	**EGE3160FFG**	**EGE3160AFG**	**EGE4160FFG**	**EGE4160AFG**

Notes

① 16, 32, 63 and 160 A are not UL listed ratings.

② Adjustable thermal are not UL listed.

③ Change the fourth digit to 7 for 100% neutral protection. Neutral is on the LH side.

EG-Frame

EG-Frame—40/35

Maximum Continuous Amps at 40 °C ①	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Adjustable ② Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Fixed Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Adjustable ② Thermal, Fixed Magnetic Catalog Number
15	**EGS1015FFG**	**EGS2015FFG**	**EGS3015FFG**	—	**EGS4015FFG**	—
16	**EGS1016FFG**	**EGS2016FFG**	**EGS3016FFG**	—	**EGS4016FFG**	—
20	**EGS1020FFG**	**EGS2020FFG**	**EGS3020FFG**	—	**EGS4020FFG**	**EGS4020AFG**
25	**EGS1025FFG**	**EGS2025FFG**	**EGS3025FFG**	**EGS3025AFG**	**EGS4025FFG**	**EGS4025AFG**
30	**EGS1030FFG**	**EGS2030FFG**	**EGS3030FFG**	—	**EGS4030FFG**	—
32	**EGS1032FFG**	**EGS2032FFG**	**EGS3032FFG**	**EGS3032AFG**	**EGS4032FFG**	**EGS4032AFG**
35	**EGS1035FFG**	**EGS2035FFG**	**EGS3035FFG**	—	**EGS4035FFG**	—
40	**EGS1040FFG**	**EGS2040FFG**	**EGS3040FFG**	**EGS3040AFG**	**EGS4040FFG**	**EGS4040AFG**
45	**EGS1045FFG**	**EGS2045FFG**	**EGS3045FFG**	—	**EGS4045FFG**	—
50	**EGS1050FFG**	**EGS2050FFG**	**EGS3050FFG**	**EGS3050AFG**	**EGS4050FFG**	**EGS4050AFG**
60	**EGS1060FFG**	**EGS2060FFG**	**EGS3060FFG**	—	**EGS4060FFG**	—
63	**EGS1063FFG**	**EGS2063FFG**	**EGS3063FFG**	**EGS3063AFG**	**EGS4063FFG**	**EGS4063AFG**
70	**EGS1070FFG**	**EGS2070FFG**	**EGS3070FFG**	—	**EGS4070FFG**	—
80	**EGS1080FFG**	**EGS2080FFG**	**EGS3080FFG**	**EGS3080AFG**	**EGS4080FFG**	**EGS4080AFG**
90	**EGS1090FFG**	**EGS2090FFG**	**EGS3090FFG**	—	**EGS4090FFG**	—
100	**EGS1100FFG**	**EGS2100FFG**	**EGS3100FFG**	**EGS3100AFG**	**EGS4100FFG**	**EGS4100AFG**
125	**EGS1125FFG**	**EGS2125FFG**	**EGS3125FFG**	**EGS3125AFG**	**EGS4125FFG**	**EGS4125AFG**
160	—	—	**EGS3160FFG**	**EGS3160AFG**	**EGS4160FFG**	**EGS4160AFG**

Notes

① 16, 32, 63 and 160 A are not UL listed ratings.

② Adjustable thermal are not UL listed.

③ Change the fourth digit to 7 for 100% neutral protection. Neutral is on the LH side.

2

EG-Frame

EG-Frame—70/65

Maximum Continuous Amps at 40 °C ①	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number	Three-Pole Adjustable ② Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Fixed Thermal, Fixed Magnetic Catalog Number	Four-Pole ③ Adjustable ② Thermal, Fixed Magnetic Catalog Number
15	EGH1015FFG	EGH2015FFG	EGH3015FFG	—	EGH4015FFG	—
16	EGH1016FFG	EGH2016FFG	EGH3016FFG	—	EGH4016FFG	—
20	EGH1020FFG	EGH2020FFG	EGH3020FFG	EGH3020AFG	EGH4020FFG	EGH4020AFG
25	EGH1025FFG	EGH2025FFG	EGH3025FFG	EGH3025AFG	EGH4025FFG	EGH4025AFG
30	EGH1030FFG	EGH2030FFG	EGH3030FFG	—	EGH4030FFG	—
32	EGH1032FFG	EGH2032FFG	EGH3032FFG	EGH3032AFG	EGH4032FFG	EGH4032AFG
35	EGH1035FFG	EGH2035FFG	EGH3035FFG	—	EGH4035FFG	—
40	EGH1040FFG	EGH2040FFG	EGH3040FFG	EGH3040AFG	EGH4040FFG	EGH4040AFG
45	EGH1045FFG	EGH2045FFG	EGH3045FFG	—	EGH4045FFG	EGH4050AFG
50	EGH1050FFG	EGH2050FFG	EGH3050FFG	EGH3050AFG	EGH4050FFG	—
60	EGH1060FFG	EGH2060FFG	EGH3060FFG	—	EGH4060FFG	—
63	EGH1063FFG	EGH2063FFG	EGH3063FFG	EGH3063AFG	EGH4063FFG	EGH4063AFG
70	EGH1070FFG	EGH2070FFG	EGH3070FFG	—	EGH4070FFG	—
80	EGH1080FFG	EGH2080FFG	EGH3080FFG	EGH3080AFG	EGH4080FFG	EGH4080AFG
90	EGH1090FFG	EGH2090FFG	EGH3090FFG	—	EGH4090FFG	—
100	EGH1100FFG	EGH2100FFG	EGH3100FFG	EGH3100AFG	EGH4100FFG	EGH4100AFG
125	EGH1125FFG	EGH2125FFG	EGH3125FFG	EGH3125AFG	EGH4125FFG	EGH4125AFG

Notes

① 16, 32, 63A are not UL listed ratings.
② Adjustable thermal are not UL listed.
③ Change the fourth digit to 7 for 100% neutral protection. Neutral is on the LH side.

EG-Frame—100/100 Current Limiting (Single-Pole and Two-Pole Unavailable)

EG-Frame

EG-Frame—100/100

	Three-Pole		Four-Pole 0% Protected Neutral ③	
	Fixed Thermal, Fixed Magnetic	Adjustable ② Thermal, Fixed Magnetic	Fixed Thermal, Fixed Magnetic	Adjustable ② Thermal, Fixed Magnetic
Maximum Continuous Amps at 40 °C ①	Catalog Number	Catalog Number	Catalog Number	Catalog Number
15	**EGC3015FFG**	—	**EGC7015FFG**	—
16	**EGC3016FFG**	—	**EGC7016FFG**	—
20	**EGC3020FFG**	**EGC3020AFG**	**EGC7020FFG**	**EGC7020AFG**
25	**EGC3025FFG**	**EGC3025AFG**	**EGC7025FFG**	**EGC7025AFG**
30	**EGC3030FFG**	—	**EGC7030FFG**	—
32	**EGC3032FFG**	**EGC3032AFG**	**EGC7032FFG**	**EGC7032AFG**
35	**EGC3035FFG**	—	**EGC7035FFG**	—
40	**EGC3040FFG**	**EGC3040AFG**	**EGC7040FFG**	**EGC7040AFG**
45	**EGC3045FFG**	—	**EGC7045FFG**	—
50	**EGC3050FFG**	**EGC3050AFG**	**EGC7050FFG**	**EGC7050AFG**
60	**EGC3060FFG**	—	**EGC7060FFG**	—
63	**EGC3063FFG**	**EGC3063AFG**	**EGC7063FFG**	**EGC7063AFG**
70	**EGC3070FFG**	—	**EGC7070FFG**	—
80	**EGC3080FFG**	**EGC3080AFG**	**EGC7080FFG**	**EGC7080AFG**
90	**EGC3090FFG**	—	**EGC7090FFG**	—
100	**EGC3100FFG**	**EGC3100AFG**	**EGC7100FFG**	**EGC7100AFG**
125	**EGC3125FFG**	**EGC3125AFG**	**EGC7125FFG**	**EGC7125AFG**

Molded Case Switches ④

Catalog Number
EGK3125KSG
EGK7125KSG
EGK3160KSG
EGK7160KSG

Notes

① 16, 32, 63A are not UL listed ratings.
② Adjustable thermal is not UL listed.
③ Change the fourth digit to 7 for 100% neutral protection. Neutral is on LH side.
④ Molded case switches may open above 1250 A.

EG Bolt-On Complete Breaker (Includes Frame, Trip Unit and Mounting Hardware)

EG-Frame

EG-Frame—18 kAIC at 480 Vac

Maximum Continuous Amps at 40 °C	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number ①	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number ②	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number ③
15	**EGB1015FFB**	**EGB2015FFB**	**EGB3015FFB**
20	**EGB1020FFB**	**EGB2020FFB**	**EGB3020FFB**
25	**EGB1025FFB**	**EGB2025FFB**	**EGB3025FFB**
30	**EGB1030FFB**	**EGB2030FFB**	**EGB3030FFB**
35	**EGB1035FFB**	**EGB2035FFB**	**EGB3035FFB**
40	**EGB1040FFB**	**EGB2040FFB**	**EGB3040FFB**
45	**EGB1045FFB**	**EGB2045FFB**	**EGB3045FFB**
50	**EGB1050FFB**	**EGB2050FFB**	**EGB3050FFB**
60	**EGB1060FFB**	**EGB2060FFB**	**EGB3060FFB**
70	**EGB1070FFB**	**EGB2070FFB**	**EGB3070FFB**
80	**EGB1080FFB**	**EGB2080FFB**	**EGB3080FFB**
90	**EGB1090FFB**	**EGB2090FFB**	**EGB3090FFB**
100	**EGB1100FFB**	**EGB2100FFB**	**EGB3100FFB**
110	**EGB1110FFB**	**EGB2110FFB**	**EGB3110FFB**
125	**EGB1125FFB**	**EGB2125FFB**	**EGB3125FFB**

EG-Frame

EG-Frame—35 kAIC at 480 Vac

Maximum Continuous Amps at 40 °C	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number ①	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number ②	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number ③
15	**EGS1015FFB**	**EGS2015FFB**	**EGS3015FFB**
20	**EGS1020FFB**	**EGS2020FFB**	**EGS3020FFB**
25	**EGS1025FFB**	**EGS2025FFB**	**EGS3025FFB**
30	**EGS1030FFB**	**EGS2030FFB**	**EGS3030FFB**
35	**EGS1035FFB**	**EGS2035FFB**	**EGS3035FFB**
40	**EGS1040FFB**	**EGS2040FFB**	**EGS3040FFB**
45	**EGS1045FFB**	**EGS2045FFB**	**EGS3045FFB**
50	**EGS1050FFB**	**EGS2050FFB**	**EGS3050FFB**
60	**EGS1060FFB**	**EGS2060FFB**	**EGS3060FFB**
70	**EGS1070FFB**	**EGS2070FFB**	**EGS3070FFB**
80	**EGS1080FFB**	**EGS2080FFB**	**EGS3080FFB**
90	**EGS1090FFB**	**EGS2090FFB**	**EGS3090FFB**
100	**EGS1100FFB**	**EGS2100FFB**	**EGS3100FFB**
110	**EGS1110FFB**	**EGS2110FFB**	**EGS3110FFB**
125	**EGS1125FFB**	**EGS2125FFB**	**EGS3125FFB**

Notes

① For bulk pack 24, add suffix BP24 and order quantities of 24.
② For bulk pack 12, add suffix BP12 and order quantities of 12.
③ For bulk pack 8, add suffix BP8 and order quantities of 8.

EG-Frame

EG-Frame—65 kAIC at 480 Vac

Maximum Continuous Amps at 40 °C	Single-Pole Fixed Thermal, Fixed Magnetic Catalog Number ①	Two-Pole Fixed Thermal, Fixed Magnetic Catalog Number ②	Three-Pole Fixed Thermal, Fixed Magnetic Catalog Number ③
15	**EGH1015FFB**	**EGH2015FFB**	**EGH3015FFB**
20	**EGH1020FFB**	**EGH2020FFB**	**EGH3020FFB**
25	**EGH1025FFB**	**EGH2025FFB**	**EGH3025FFB**
30	**EGH1030FFB**	**EGH2030FFB**	**EGH3030FFB**
35	**EGH1035FFB**	**EGH2035FFB**	**EGH3035FFB**
40	**EGH1040FFB**	**EGH2040FFB**	**EGH3040FFB**
45	**EGH1045FFB**	**EGH2045FFB**	**EGH3045FFB**
50	**EGH1050FFB**	**EGH2050FFB**	**EGH3050FFB**
60	**EGH1060FFB**	**EGH2060FFB**	**EGH3060FFB**
70	**EGH1070FFB**	**EGH2070FFB**	**EGH3070FFB**
80	**EGH1080FFB**	**EGH2080FFB**	**EGH3080FFB**
90	**EGH1090FFB**	**EGH2090FFB**	**EGH3090FFB**
100	**EGH1100FFB**	**EGH2100FFB**	**EGH3100FFB**
110	**EGH1110FFB**	**EGH2110FFB**	**EGH3110FFB**
125	**EGH1125FFB**	**EGH2125FFB**	**EGH3125FFB**

Load Terminals

Maximum Breaker Amps	Terminal, Body Material	Wire Type	Metric Wire Range mm^2	AWG Wire Range	(Package of Three Terminals) Catalog Number
Standard Cu/Al Pressure Type Terminals					
15–50	Aluminum	Cu/Al	2.5–50	#14–1/0	**3TA125EF**
60–125	Aluminum	Cu/Al	16–70	#6–3/0	**3TA150EF**

Notes

① For bulk pack 24, add suffix BP24 and order quantities of 24.
② For bulk pack 12, add suffix BP12 and order quantities of 12.
③ For bulk pack 8, add suffix BP8 and order quantities of 8.

Accessories Selection Guide and Ordering Information

EG-Frame



3T125EF



3TA125EF



3TA150EF



3TA160EFK



EF2RTWK, Two-Pole–Metric
EF3RTWK, Three-Pole–Metric
EF4RTWK, Four-Pole–Metric
EF2RTDK, Two-Pole–Imperial
EF3RTDK, Three-Pole–Imperial
EF4RTDK, Four-Pole–Imperial

Control Wire Terminal Kit GCWTK



Multiwire Connectors

Line and Load Terminals

Maximum Breaker Amps	Terminal Body Material	Wire Type	Metric Wire Range mm²	AWG Wire Range	(Package of Three Terminals) Catalog Number
Standard Cu/Al Pressure Type Terminals					
125	Steel	Al	4–6	#14-3/0	**3T125EF** ①
125	Steel	Cu	2.5–95	#14-3/0	**3T125EF** ①
125	Aluminum	Cu/Al	2.5–50	#14-1/0	**3TA125EF**
160	Aluminum	Cu/Al	16–70	#6-3/0	**3TA150EF**
160	Aluminum	Cu/Al	35–120	#3-250	**3TA160EFK**
160	Aluminum	Cu/Al	35–120	#3-250	**4TA160EFK** ②

EG-Frame circuit breakers and molded case switches have line and load terminals as standard equipment.

Insert collar enclosing conductor as shown. Locate nut on top of conductor and tighten securely with screw and washer.

Caution: Collar must surround conductor.

Insert collar enclosing conductor and center on extrusion. Tighten securely with screw and washer. Endcap kits are used on the E-Frame breaker line side to connect busbar or similar electrical connections. Includes hardware.

Notes

① Standard line and load terminals.
② Four-pole kit with four terminals.

Control Wire Terminal Kit

	Catalog Number
Control wire terminal kit	**5652B38G01**
Package of 12—priced individually	

For use with steel or stainless steel standard line and load terminals only.

Interphase Barriers

	Catalog Number
Interphase barriers	**EIPBK**
Package of 12—priced individually	

The interphase barrier is available for extended insulation between circuit breaker poles. Specify quantity when ordering.

Base Mounting Hardware—DIN Rail Mounting

	Catalog Number
DIN rail adapter—single-pole	**EF1DIN**
DIN rail adapter—two-pole	**EGDIN**
DIN rail adapter—three- or four-pole	**EF34DIN**
Metal DIN rail adapter—three-pole	**EGGDDIN**

Metric base mounting hardware is included with a circuit breaker or molded case switch. (Included with breaker.) If required separately, order S/N 8703C80G08.

Note: English mounting hardware kit can be supplied separate. Catalog number is **BMHE** #6–32 x 3 inches for two-, three- and four-pole. Single-pole mounting hardware metric order **8703C80G11**. English hardware **8703C80G12**. Both sold in quantities of 100.

Terminal Shields

The terminal shield is available for line terminal areas in three- and four-pole circuit breakers. Special terminal shields are also available for use when an electrical (solenoid) operator is mounted on the circuit breaker. The standard style number by pole for each terminal shield is for a package of 10 and is priced per each package. Special terminal shields are packaged individually.

Terminal Shields—IP30 Protection

Number of Poles	Catalog Number
3	**EFTS3K**
4	**EFTS4K**

Terminal End Covers (Gas Barrier)

The terminal end cover is available for three-pole circuit breakers only. Two conductor opening sizes are available. Specify quantity (one per circuit breaker) when ordering.

Terminal End Covers

Conductor Opening Diameter Inches (mm)	Catalog Number
6.35 (0.25)	**EEC3K**
10.41 (0.41)	**EEC4K**

Multiwire Connectors

Field-installed multiwire connectors for the load side (OFF) end terminals. They are used to distribute the load from the circuit breaker to multiple devices without the use of separate distribution terminal blocks.

Multiwire lug kits include mounting hardware, terminal shield insulators and tin-plated aluminum connectors to replace three mechanical load lugs. UL listed as used on the load side (OFF) end.

EG-Frame Multiwire Connectors Ordering Information (Package of 3) ①

Maximum Amperes	Wires per Terminal	Wire Size Range AWG Cu	Kit Catalog Number
125	3	14–2	**3TA125E3K**
125	6	14–6	**3TA125E6K**

Note

① For four-pole kit, change "3" at beginning of catalog number to "4."

Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

EG-Frame Accessories

Description	Reference Page	Single-Pole	Two-Pole		Three-Pole			Four-Pole			
		Center	Left	Right	Left	Center	Right	Left	Center	Right	Neutral
Internal Accessories (Only one internal accessory per pole)											
Alarm lockout (Make/Break)	**V4-T2-109**	—	—	■	—	—	■	—	—	■	—
Alarm lockout (2Make/2Break)	**V4-T2-109**	—	—	■	—	—	■	—	—	■	—
Auxiliary switch (1A, 1B)	**V4-T2-109**	—	—	■	—	—	■	—	—	■	—
Auxiliary switch (2A, 2B)	**V4-T2-109**	—	—	■	—	—	■	—	—	■	—
Auxiliary switch and alarm switch combination	**V4-T2-109**	—	—	■	—	—	■	—	—	■	—
Shunt trip—standard	**V4-T2-109**	—	—	—	■	—	—	■	—	—	—
Undervoltage release mechanism	**V4-T2-110**	—	—	—	■	—	—	■	—	—	—
External Accessories											
End cap kit	**V4-T2-25**	—	●	●	●	●	●	●	●	●	●
Control wire terminal kit	**V4-T2-25**	●	●	●	●	●	●	●	●	●	●
Multiwire connectors	**V4-T2-25**	●	●	●	●	●	●	●	●	●	●
Base mounting hardware	**V4-T2-25**	●	●	●	●	●	●	●	●	●	●
Terminal shields	**V4-T2-25**	●	●	●	●	●	●	●	●	●	●
Terminal end covers	**V4-T2-25**	—	—	—	●	●	●	—	—	—	—
Interphase barriers	**V4-T2-25**	—	●	●	●	●	●	●	●	●	●
Non-padlockable handle block	**V4-T2-107**	■	■	—	—	■	—	—	■	—	—
Snap-on padlockable handle lock hasp	**V4-T2-107**	■	■	—	—	■	—	—	■	—	—
Padlockable handle lock hasp	**V4-T2-107**	—	—	■	❑	—	❑	❑	—	❑	—
Walking beam interlock—requires two breakers	**V4-T2-107**	—	—	—	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-107**	—	●	●	●	●	●	●	●	●	●
Electrical operator	**V4-T2-107**	—	—	—	●	●	●	—	—	—	—
Handle mechanisms	**V4-T2-415**	—	—	—	●	●	●	—	—	—	—
Modifications (Refer to Eaton)											
Moisture fungus treatment	**V4-T2-105**	●	●	●	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●	●	●	●
Marine/naval application, UL 489 Supplement SA and SB	—	●	●	●	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Technical Data and Specifications

UL 489/IEC 60947-2 Interrupting Capacity (Symmetrical Amperes) (kA) Ratings

Circuit Breaker Type	Number of Poles	Volts AC (50/60 Hz) 120	220–240 I_{cu}	220–240 I_{cs}	277	347	380–415 I_{cu}	380–415 I_{cs}	480	600Y/347	690 ② I_{cu}	690 ② I_{cs}	Volts DC ① 125 I_{cu}	125 I_{cs}	250 ③④ I_{cu}	250 ③④ I_{cs}
EGB125	1	35	25	25	18	—	—	—	—	—	—	—	10	10	—	—
	2, 3, 4	—	25	25	—	—	18	18	18	—	—	—	—	—	10	10
EGE125	2, 3, 4	—	35	35	—	—	25	25	25	18	—	—	—	—	10	10
EGS125	1	100	85	43	35	22	—	—	—	—	—	—	35	35	—	—
	2, 3, 4	—	85	43	—	—	40	30	35	22	—	—	—	—	35	35
EGH125	1	200	100	50	65	25	—	—	—	—	—	—	42	42	—	—
	2, 3, 4	—	100	50	—	—	70	35	65	25	—	—	—	—	42	42
EGC125 ⑤	3, 4	—	200	200	—	—	100	100	100	35	—	—	—	—	42	42
EGB160 ②	3, 4	—	25	25	—	—	18	18	18	—	—	—	—	—	10	10
EGE160 ②	3, 4	—	35	35	—	—	25	25	25	18	—	—	—	—	10	10
EGS160 ②	3, 4	—	85	43	—	—	40	30	35	22	—	—	—	—	35	35

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
EGC	240 V/200 kA	24.5	0.6310
EGC	480 V/100 kA	24.5	0.6310
EGC	600 Y/35 kA	20.0	1.392

Dimensions and Weights

Approximate Dimensions in Inches (mm)

EG-Frame

Number of Poles	Width	Height	Depth
1	1.00 (25.4)	5.50 (139.7)	2.99 (75.9)
2	2.00 (50.8)	5.50 (139.7)	2.99 (75.9)
3	3.00 (76.2)	5.50 (139.7)	2.99 (75.9)
4	4.00 (101.6)	5.50 (139.7)	2.99 (75.9)

EG-Frame

Front Cover Cutout



Front View Three-Pole



Side View



Approximate Shipping Weight in Lbs (kg)

EG-Frame

EG Breaker Type	Number of Poles 1	2	3	4
EGB125	1.5 (0.68)	2.0 (0.91)	3.0 (1.36)	4.9 (1.82)

Notes

① DC ratings apply to substantially non-inductive circuits.
② IEC only.
③ Two-pole circuit breaker, or two poles of three-pole circuit breaker.
④ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at 42 kA.
⑤ Current limiting per UL 489.

2

EG-Frame With Earth Leakage Module



EG-Frame With Current Limiter Module



JG-Frame (63–250 Amperes)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	
Catalog Number Selection	**V4-T2-30**
Product Selection	**V4-T2-31**
Accessories	**V4-T2-42**
Technical Data and Specifications	**V4-T2-43**
Dimensions and Weights	**V4-T2-45**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

JG-Frame (63–250 Amperes)

Product Description

JG breaker is HACR rated.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

2

Series G—JG-Frame (63–250 Amperes)

J G S 3 250 FA G C

Frame
J

Standard/Application
G = IEC/CE/UL/CSA

Performance

	600	480	415	240
E	18	25	25	65
S	18	35	40	85
H	25	65	70	100
C	35	100	100	200
U	50	150	150	200
X	50	200	200	200
K	Molded case switch			

Number of Poles
2 = Two
3 = Three
4 = Four—Neutral 0% Protected
9 = Four—Neutral 100% Protected

Amperes
050
070
080
090
100
125
150
160
175
200
225
250

Trip Unit
AA = Adj. adj.
FA = Fixed adj.
KS = Molded case switch
33 = 310+ electronic LS
32 = 310+ electronic LSI
35 = 310+ electronic LSG
36 = 310+ electronic LSIG
NN = Frame only (250 A only; no trip unit)

Terminations/Hardware

Terminals	Mounting Hardware
M = Metric end caps	Metric
E = Imperial end caps	Imperial
G = Line/load standard	Metric
W = Without terminals	

Rating
Blank = 80% rated
C = 100% rated
F01 = Freeze tested for –70ºF (–57ºC)
F02 = Freeze tested for –22ºF (–30ºC)

Trip Unit

JT 4 100 FA B20

Trip
JT

Number of Poles
2 = Two
3 = Three
4 = Four—Neutral 0% Protected
9 = Four—Neutral 100% Protected

Amperes

T/M	ETU
080	**050**
090	**100**
100	**160**
110	**250**
125	
150	
160	
175	
200	
225	
250	

Trip Unit
AA = Adj. adj.
FA = Fixed adj.
KS = Molded case switch
33 = 310+ electronic LS
32 = 310+ electronic LSI
35 = 310+ electronic LSG
36 = 310+ electronic LSIG

Features (ETU Only) ①②
Blank= No feature
B20 = High load alarm
B21 = Ground fault alarm, with trip
B22 = Ground fault alarm, no trip
ZG = Zone selective interlocking

Notes

① Bxx features cannot be combined with other Bxx features.
② B21 and B22 available with LSG and LSIG trip units.

Product Selection

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware)—IC Rating at 415/480 Volts

JG-Frame

JG-Frame—IEC/CE/UL/CSA—25/25

Maximum Continuous Amperes	Magnetic Range	Two-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Adjustable Magnetic ① Catalog Number	Four-Pole 0%② Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Adjustable Magnetic ① Catalog Number
70	350–700	**JGE2070FAG**	**JGE3070FAG**	—	**JGE4070FAG**	—
90	450–900	**JGE2090FAG**	**JGE3090FAG**	—	**JGE4090FAG**	—
100	500–1000	**JGE2100FAG**	**JGE3100FAG**	**JGE3100AAG**	**JGE4100FAG**	**JGE4100AAG**
125	625–1250	**JGE2125FAG**	**JGE3125FAG**	**JGE3125AAG**	**JGE4125FAG**	**JGE4125AAG**
150	750–1550	**JGE2150FAG**	**JGE3150FAG**	—	**JGE4150FAG**	—
160	800–1600	—	—	**JGE3160AAG**	—	**JGE4160AAG**
175	875–1750	**JGE2175FAG**	**JGE3175FAG**	—	**JGE4175FAG**	—
200	1000–2000	**JGE2200FAG**	**JGE3200FAG**	**JGE3200AAG**	**JGE4200FAG**	**JGE4200AAG**
225	1125–2250	**JGE2225FAG**	**JGE3225FAG**	—	**JGE4225FAG**	—
250	1250–2500	**JGE2250FAG**	**JGE3250FAG**	**JGE3250AAG**	**JGE4250FAG**	**JGE4250AAG**

JG-Frame

JG-Frame—IEC/CE/UL/CSA—40/35, Two-Pole

Maximum Continuous Amperes	Magnetic Range	Two-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Adjustable Magnetic ① Catalog Number	Four-Pole 0%② Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Adjustable Magnetic ① Catalog Number
70	350–700	**JGS2070FAG**	**JGS3070FAG**	—	**JGS4070FAG**	—
90	450–900	**JGS2090FAG**	**JGS3090FAG**	—	**JGS4090FAG**	—
100	500–1000	**JGS2100FAG**	**JGS3100FAG**	**JGS3100AAG**	**JGS4100FAG**	**JGS4100AAG**
125	625–1250	**JGS2125FAG**	**JGS3125FAG**	**JGS3125AAG**	**JGS4125FAG**	**JGS4125AAG**
150	750–1550	**JGS2150FAG**	**JGS3150FAG**	—	**JGS4150FAG**	—
160	800–1600	—	—	**JGS3160AAG**	—	**JGS4160AAG**
175	875–1750	**JGS2175FAG**	**JGS3175FAG**	—	**JGS4175FAG**	—
200	1000–2000	**JGS2200FAG**	**JGS3200FAG**	**JGS3200AAG**	**JGS4200FAG**	**JGS4200AAG**
225	1125–2250	**JGS2225FAG**	**JGS3225FAG**	—	**JGS4225FAG**	—
250	1250–2500	**JGS2250FAG**	**JGS3250FAG**	**JGS3250AAG**	**JGS4250FAG**	**JGS4250AAG**

Notes

① EC-EN 60947-2 only. Adjustment is 0.8 and 1.0.

② 9 for 0–100% neutral protection. Neutral is on LH side.

2

JG-Frame

JG-Frame—IEC/CE/UL/CSA—70/65

Maximum Continuous Amperes	Magnetic Range	Two-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Fixed Magnetic ① Catalog Number	Four-Pole 0%② Fixed Thermal, Adjustable Magnetic Catalog Number	Adjustable Thermal, Fixed Magnetic ① Catalog Number
70	350–700	**JGH2070FAG**	**JGH3070FAG**	—	**JGH4070FAG**	—
90	450–900	**JGH2090FAG**	**JGH3090FAG**	—	**JGH4090FAG**	—
100	500–1000	**JGH2100FAG**	**JGH3100FAG**	**JGH3100AAG**	**JGH4100FAG**	**JGH4100AAG**
125	625–1250	**JGH2125FAG**	**JGH3125FAG**	**JGH3125AAG**	**JGH4125FAG**	**JGH4125AAG**
150	750–1550	**JGH2150FAG**	**JGH3150FAG**	—	**JGH4150FAG**	—
160	800–1600	—	—	**JGH3160AAG**	—	**JGH4160AAG**
175	875–1750	**JGH2175FAG**	**JGH3175FAG**	—	**JGH4175FAG**	—
200	1000–2000	**JGH2200FAG**	**JGH3200FAG**	**JGH3200AAG**	**JGH4200FAG**	**JGH4200AAG**
225	1125–2250	**JGH2225FAG**	**JGH3225FAG**	—	**JGH4225FAG**	—
250	1250–2500	**JGH2250FAG**	**JGH3250FAG**	**JGH3250AAG**	**JGH4250FAG**	**JGH4250AAG**

Notes

① EC-EN 60947-2 only. Adjustment is 0.8 and 1.0.

② 9 for 0–100% neutral protection. Neutral is on LH side.

Two-Pole not available in IEC/CE/UL/CSA 100/100, 150/150

JG-Frame

JG-Frame—IEC/CE/UL/CSA—100/100, Current Limiting

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Adjustable Thermal, Adjustable Magnetic ① Catalog Number	Four-Pole 0% ② Fixed Thermal, Adjustable Magnetic Catalog Number	Four-Pole 0% ② Adjustable Thermal, Adjustable Magnetic ① Catalog Number
70	350–700	**JGC3070FAG**	—	**JGC4070FAG**	—
80	400–800	—	**JGC3080AAG**	—	**JGC4080AAG**
90	450–900	**JGC3090FAG**	—	**JGC4090FAG**	—
100	500–1000	**JGC3100FAG**	**JGC3100AAG**	**JGC4100FAG**	**JGC4100AAG**
125	625–1250	**JGC3125FAG**	**JGC3125AAG**	**JGC4125FAG**	**JGC4125AAG**
150	750–1550	**JGC3150FAG**	—	**JGC4150FAG**	—
160	800–1600	—	**JGC3160AAG**	—	**JGC4160AAG**
175	875–1750	**JGC3175FAG**	—	**JGC4175FAG**	—
200	1000–2000	**JGC3200FAG**	**JGC3200AAG**	**JGC4200FAG**	**JGC4200AAG**
225	1125–2250	**JGC3225FAG**	—	**JGC4225FAG**	—
250	1250–2500	**JGC3250FAG**	**JGC3250AAG**	**JGC4250FAG**	**JGC4250AAG**

JG-Frame

JG-Frame—IEC/CE/UL/CSA—150/150, Current Limiting

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Adjustable Thermal, Adjustable Magnetic ① Catalog Number	Four-Pole 0% ② Fixed Thermal, Adjustable Magnetic Catalog Number	Four-Pole 0% ② Adjustable Thermal, Adjustable Magnetic ① Catalog Number
70	350–700	**JGU3070FAG**	—	**JGU4070FAG**	—
80	400–800	—	**JGU3080AAG**	—	**JGU4080AAG**
90	450–900	**JGU3090FAG**	—	**JGU4090FAG**	—
100	500–1000	**JGU3100FAG**	**JGU3100AAG**	**JGU4100FAG**	**JGU4100AAG**
125	625–1250	**JGU3125FAG**	**JGU3125AAG**	**JGU4125FAG**	**JGU4125AAG**
150	750–1550	**JGU3150FAG**	—	**JGU4150FAG**	—
160	800–1600	—	**JGU3160AAG**	—	**JGU4160AAG**
175	875–1750	**JGU3175FAG**	—	**JGU4175FAG**	—
200	1000–2000	**JGU3200FAG**	**JGU3200AAG**	**JGU4200FAG**	**JGU4200AAG**
225	1125–2250	**JGU3225FAG**	—	**JGU4225FAG**	—
250	1250–2500	**JGU3250FAG**	**JGU3250AAG**	**JGU4250FAG**	**JGU4250AAG**

Notes

① EC-EN 60947-2 only. Adjustment is 0.8 and 1.0.

② 9 for 0–100% neutral protection. Neutral is on LH side.

Two-Pole not available in IEC/CE/UL/CSA 200/200

JG-Frame

JG-Frame—IEC/CE/UL/CSA 200/200, Current Limiting

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number	Three-Pole Adjustable Thermal, Adjustable Magnetic ① Catalog Number	Four-Pole ② Fixed Thermal, Adjustable Magnetic Catalog Number	Four-Pole ② Adjustable Thermal, Adjustable Magnetic ① Catalog Number
70	350–700	**JGX3070FAG**	—	**JGX4070FAG**	—
80	400–800	—	**JGX3080AAG**	—	**JGX4080AAG**
90	450–900	**JGX3090FAG**	—	**JGX4090FAG**	—
100	500–1000	**JGX3100FAG**	**JGX3100AAG**	**JGX4100FAG**	**JGX4100AAG**
125	625–1250	**JGX3125FAG**	**JGX3125AAG**	**JGX4125FAG**	**JGX4125AAG**
150	750–1550	**JGX3150FAG**	—	**JGX4150FAG**	—
160	800–1600	—	**JGX3160AAG**	—	**JGX4160AAG**
175	875–1750	**JGX3175FAG**	—	**JGX4175FAG**	—
200	1000–2000	**JGX3200FAG**	**JGX3200AAG**	**JGX4200FAG**	**JGX4200AAG**
225	1125–2250	**JGX3225FAG**	—	**JGX4225FAG**	—
250	1250–2500	**JGX3250FAG**	**JGX3250AAG**	**JGX4250FAG**	**JGX4250AAG**

Molded Case Switches ③

Catalog Number
JGK3250KSG
JGK7250KSG

Notes

① EC-EN 60947-2 only. Adjustment is 0.8 and 1.0.

② 9 for 0–100% neutral protection. Neutral is on LH side.

③ Molded case switches will trip above 2500 amperes.

Frame—IC Rating at 415/480 Volts

Maximum Amperes	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole 0% Catalog Number
25/25			
250	**JGE2250NN**	**JGE3250NN**	**JGE4250NN**
40/35			
250	**JGS2250NN**	**JGS3250NN**	**JGS4250NN**
70/65			
250	**JGH2250NN**	**JGH3250NN**	**JGH4250NN**
100/100 Current Limiting Per UL 489			
250	—	**JGC3250NN**	**JGC4250NN**
150/150 Current Limiting Per UL 489			
250	—	**JGU3250NN**	**JGU4250NN**
200/200 Current Limiting Per UL 489			
250	—	**JGX3250NN**	**JGX4250NN**
25/25 100% Rated Per UL 489 ②			
250	—	**JGE3250NNC**	—
40/35 100% Rated Per UL 489 ②			
250	—	**JGS3250NNC**	—
70/65 100% Rated Per UL 489 ②			
250	—	**JGH3250NNC**	—

Thermal-Magnetic Trip Unit

Ampere Rating	Range	Catalog Number			Range	Catalog Number	
70	350–700	**JT2070FA**	**JT3070FA**	—	—	**JT4070FA**	—
80	400–800	—	**JT3080FA**	**JT3080AA** ③	64–100	—	**JT4080AA** ③
90	450–900	**JT2090FA**	**JT3090FA**	—	—	**JT4090FA**	—
100	500–1000	**JT2100FA**	**JT3100FA**	**JT3100AA** ③	80–100	**JT4100FA**	**JT4100AA** ③
125	625–1250	**JT2125FA**	**JT3125FA**	**JT3125AA** ③	100–125	**JT4125FA**	**JT4125AA** ③
150	750–1550	**JT2150FA**	**JT3150FA**	—	—	**JT4150FA**	—
160	800–1600	—	—	**JT3160AA** ③	128–160	—	**JT4160AA** ③
175	875–1750	**JT2175FA**	**JT3175FA**	—	—	**JT4175FA**	—
200	1000–2000	**JT2200FA**	**JT3200FA**	**JT3200AA** ③	160–200	**JT4200FA**	**JT4200AA** ③
225	1125–2250	**JT2225FA**	**JT3225FA**	—	—	**JT4225FA**	—
250	1250–2500	**JT2250FA**	**JT3250FA**	**JT3250AA** ③	200–250	**JT4250FA**	**JT4250AA** ③

Notes

① Standard line and load terminals.

② Components—100% rated frame.

③ Adjustable thermal trip units are typically used in IEC markets and are not UL or CSA listed.

310+ Electronic Trip Units

See 310+ adjustability specifications on **Page V4-T2-44**.

JG 310+ Electronic Trip Units

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JT305033**	**JT305032**	**JT305035**	**JT305036**	**JGFCT050**
100	**JT310033**	**JT310032**	**JT310035**	**JT310036**	**JGFCT100**
160	**JT316033**	**JT316032**	**JT316035**	**JT316036**	**JGFCT160**
250	**JT325033**	**JT325032**	**JT325035**	**JT325036**	**JGFCT250**
Four-Pole ②③					
50	**JT405033**	**JT405032**	**JT405035**	**JT405036**	—
100	**JT410033**	**JT410032**	**JT410035**	**JT410036**	—
160	**JT416033**	**JT416032**	**JT416035**	**JT416036**	—
250	**JT425033**	**JT425032**	**JT425035**	**JT425036**	—

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V**
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor (250 A)	**JGFCT250**
External neutral sensor (160 A)	**JGFCT160**
External neutral sensor (100 A)	**JGFCT100**
External neutral sensor (80 A)	**JGFCT050**
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06**

Notes

① For use on a three-pole breaker used in a four-wire system if ground fault protection for the neutral is required.

② Neutral protection 4 = 0%, 7 = 100% electronic trip unit neutral protection is not adjustable.

③ Four-pole breakers with LSG and LSIG trip units are only available with 0% neutral protection.

Complete Breaker with 310+ Electronic Trip Units

See 310+ adjustability specifications on **Page V4-T2-44**.

IEC/UL/CSA—25/25

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGE305033G**	**JGE305032G**	**JGE305035G**	**JGE305036G**	**JGFCT050**
100	**JGE310033G**	**JGE310032G**	**JGE310035G**	**JGE310036G**	**JGFCT100**
160	**JGE316033G**	**JGE316032G**	**JGE316035G**	**JGE316036G**	**JGFCT160**
250	**JGE325033G**	**JGE325032G**	**JGE325035G**	**JGE325036G**	**JGFCT250**
Four-Pole ②					
50	**JGE405033G**	**JGE405032G**	**JGE405035G**	**JGE405036G**	—
100	**JGE410033G**	**JGE410032G**	**JGE410035G**	**JGE410036G**	—
160	**JGE416033G**	**JGE416032G**	**JGE416035G**	**JGE416036G**	—
250	**JGE425033G**	**JGE425032G**	**JGE425035G**	**JGE425036G**	—

IEC/UL/CSA—40/35

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGS305033G**	**JGS305032G**	**JGS305035G**	**JGS305036G**	**JGFCT050**
100	**JGS310033G**	**JGS310032G**	**JGS310035G**	**JGS310036G**	**JGFCT100**
160	**JGS316033G**	**JGS316032G**	**JGS316035G**	**JGS316036G**	**JGFCT160**
250	**JGS325033G**	**JGS325032G**	**JGS325035G**	**JGS325036G**	**JGFCT250**
Four-Pole ②③					
50	**JGS405033G**	**JGS405032G**	**JGS405035G**	**JGS405036G**	—
100	**JGS410033G**	**JGS410032G**	**JGS410035G**	**JGS410036G**	—
160	**JGS416033G**	**JGS416032G**	**JGS416035G**	**JGS416036G**	—
250	**JGS425033G**	**JGS425032G**	**JGS425035G**	**JGS425036G**	—

IEC/UL/CSA—70/65

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGH305033G**	**JGH305032G**	**JGH305035G**	**JGH305036G**	**JGFCT050**
100	**JGH310033G**	**JGH310032G**	**JGH310035G**	**JGH310036G**	**JGFCT100**
160	**JGH316033G**	**JGH316032G**	**JGH316035G**	**JGH316036G**	**JGFCT160**
250	**JGH325033G**	**JGH325032G**	**JGH325035G**	**JGH325036G**	**JGFCT250**
Four-Pole ②					
50	**JGH405033G**	**JGH405032G**	**JGH405035G**	**JGH405036G**	—
100	**JGH410033G**	**JGH410032G**	**JGH410035G**	**JGH410036G**	—
160	**JGH416033G**	**JGH416032G**	**JGH416035G**	**JGH416036G**	—
250	**JGH425033G**	**JGH425032G**	**JGH425035G**	**JGH425036G**	—

Notes

① Required for four-wire systems if neutral protection is required.

② Neutral protection 4 = 0%, 7 = 100% electronic trip unit neutral protection is not adjustable.

③ Four-pole breakers with LSG and LSIG trip units are only available with 0% neutral protection.

IEC/UL/CSA—100/100, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGC305033G**	**JGC305032G**	**JGC305035G**	**JGC305036G**	**JGFCT050**
100	**JGC310033G**	**JGC310032G**	**JGC310035G**	**JGC310036G**	**JGFCT100**
160	**JGC316033G**	**JGC316032G**	**JGC316035G**	**JGC316036G**	**JGFCT160**
250	**JGC335033G**	**JGC325032G**	**JGC325035G**	**JGC325036G**	**JGFCT250**
Four-Pole ②					
50	**JGC405033G**	**JGC405032G**	**JGC405035G**	**JGC405036G**	—
100	**JGC410033G**	**JGC410032G**	**JGC410035G**	**JGC410036G**	—
160	**JGC416033G**	**JGC416032G**	**JGC416035G**	**JGC416036G**	—
250	**JGC435033G**	**JGC425032G**	**JGC425035G**	**JGC425036G**	—

IEC/UL/CSA—150/150, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGU305033G**	**JGU305032G**	**JGU305035G**	**JGU305036G**	**JGFCT050**
100	**JGU310033G**	**JGU310032G**	**JGU310035G**	**JGU310036G**	**JGFCT100**
160	**JGU316033G**	**JGU316032G**	**JGU316035G**	**JGU316036G**	**JGFCT160**
250	**JGU335033G**	**JGU325032G**	**JGU325035G**	**JGU325036G**	**JGFCT250**
Four-Pole ②③					
50	**JGU405033G**	**JGU405032G**	**JGU405035G**	**JGU405036G**	—
100	**JGU410033G**	**JGU410032G**	**JGU410035G**	**JGU410036G**	—
160	**JGU416033G**	**JGU416032G**	**JGU416035G**	**JGU416036G**	—
250	**JGU435033G**	**JGU425032G**	**JGU425035G**	**JGU425036G**	—

IEC/UL/CSA—200/200, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
50	**JGX305033G**	**JGX305032G**	**JGX305035G**	**JGX305036G**	**JGFCT050**
100	**JGX310033G**	**JGX310032G**	**JGX310035G**	**JGX310036G**	**JGFCT100**
160	**JGX316033G**	**JGX316032G**	**JGX316035G**	**JGX316036G**	**JGFCT160**
250	**JGX325033G**	**JGX325032G**	**JGX325035G**	**JGX325036G**	**JGFCT250**
Four-Pole ②					
50	**JGX405033G**	**JGX405032G**	**JGX405035G**	**JGX405036G**	—
100	**JGX410033G**	**JGX410032G**	**JGX410035G**	**JGX410036G**	—
160	**JGX416033G**	**JGX416032G**	**JGX416035G**	**JGX416036G**	—
250	**JGX425033G**	**JGX425032G**	**JGX425035G**	**JGX425036G**	—

Notes

① Required for four-wire systems if neutral protection is required.

② Neutral protection 4 = 0%, 7 = 100% electronic trip unit neutral protection is not adjustable.

③ Four-pole breakers with LSG and LSIG trip units are only available with 0% neutral protection.

JG 100% Rated Circuit Breaker—Thermal-Magnetic Trip Unit

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware)—IC Rating at 415/480 Volts

JG-Frame

JG-Frame—IEC/CE/UL/CSA—25/25

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number
70	350–700	**JGE3070FAGC**
90	450–900	**JGE3090FAGC**
100	500–1000	**JGE3100FAGC**
125	625–1250	**JGE3125FAGC**
150	750–1550	**JGE3150FAGC**
160	800–1600	—
175	875–1750	**JGE3175FAGC**
200	1000–2000	**JGE3200FAGC**
225	1125–2250	**JGE3225FAGC**
250	1250–2500	**JGE3250FAGC**

JG-Frame—IEC/CE/UL/CSA—70/65

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number
70	350–700	**JGH3070FAGC**
90	450–900	**JGH3090FAGC**
100	500–1000	**JGH3100FAGC**
125	625–1250	**JGH3125FAGC**
150	750–1550	**JGH3150FAGC**
160	800–1600	—
175	875–1750	**JGH3175FAGC**
200	1000–2000	**JGH3200FAGC**
225	1125–2250	**JGH3225FAGC**
250	1250–2500	**JGH3250FAGC**

JG-Frame—IEC/CE/UL/CSA—40/35

Maximum Continuous Amperes	Magnetic Range	Three-Pole Fixed Thermal, Adjustable Magnetic Catalog Number
70	350–700	**JGS3070FAGC**
90	450–900	**JGS3090FAGC**
100	500–1000	**JGS3100FAGC**
125	625–1250	**JGS3125FAGC**
150	750–1550	**JGS3150FAGC**
160	800–1600	—
175	875–1750	**JGS3175FAGC**
200	1000–2000	**JGS3200FAGC**
225	1125–2250	**JGS3225FAGC**
250	1250–2500	**JGS3250FAGC**

JG 100% Rated 310+ Electronic Trip Unit Circuit Breaker

See 310+ adjustability specifications on **Page V4-T2-44**.

IEC/UL/CSA—25/25

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
50	**JGE305033GC**	**JGE305032GC**	**JGE305035GC**	**JGE305036GC**	**JGFCT050**
100	**JGE310033GC**	**JGE310032GC**	**JGE310035GC**	**JGE310036GC**	**JGFCT100**
160	**JGE316033GC**	**JGE316032GC**	**JGE316035GC**	**JGE316036GC**	**JGFCT160**
250	**JGE325033GC**	**JGE325032GC**	**JGE325035GC**	**JGE325036GC**	**JGFCT250**

IEC/UL/CSA—40/35

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
50	**JGS305033GC**	**JGS305032GC**	**JGS305035GC**	**JGS305036GC**	**JGFCT050**
100	**JGS310033GC**	**JGS310032GC**	**JGS310035GC**	**JGS310036GC**	**JGFCT100**
160	**JGS316033GC**	**JGS316032GC**	**JGS316035GC**	**JGS316036GC**	**JGFCT160**
250	**JGS325033GC**	**JGS325032GC**	**JGS325035GC**	**JGS325036GC**	**JGFCT250**

IEC/UL/CSA—70/65

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
50	**JGH305033GC**	**JGH305032GC**	**JGH305035GC**	**JGH305036GC**	**JGFCT050**
100	**JGH310033GC**	**JGH310032GC**	**JGH310035GC**	**JGH310036GC**	**JGFCT100**
160	**JGH316033GC**	**JGH316032GC**	**JGH316035GC**	**JGH316036GC**	**JGFCT160**
250	**JGH325033GC**	**JGH325032GC**	**JGH325035GC**	**JGH325036GC**	**JGFCT250**

Note

① Required for four-wire systems if neutral protection is required.

Accessories Selection Guide and Ordering Information

JG-Frame








T250FJ	TA250FJ	Endcap Kit	Control Wire Terminal Kit	Rear Fed Terminals	Multiwire Connectors

Load and Line Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	Metric Wire Range mm^2	AWG Wire Range/ Number of Conductors	Catalog Number
Standard Pressure Type Terminals					
250	Stainless steel	Cu	25–185	#4–350 (1)	**T250FJ** ①
250	Aluminum	Cu/Al	10–185	#8–350 (1)	**TA250FJ** ①②

JG-Frame circuit breakers include aluminum terminals TA250FJ as standard. When optional stainless steel only terminals are required, order by catalog number.

Endcap Kits

	Catalog Number	
Number of Poles	Metric	Imperial
3	**FJ3RTWK**	**FJ3RTDK**
4	**FJ4RTWK**	**FJ4RTDK**

Endcap kits are used on J250-Frame breaker to connect busbar or similar electrical connections. Includes hardware.

Control Wire Terminal Kit

Description	Catalog Number
Package of 14 (priced individually)	**FJCWTK**

For use with aluminum or copper terminals only.

Rear Fed Terminals

Maximum Amperes	Wire Size Range AWG Cu	Catalog Number
250	#4–350 kcmil	**TA250JGRF**
		3TA250JGRF

Rear fed terminals allow the cable to connect to the breaker from the back instead of the top. Terminal shields or interphase barriers are included with each rear fed terminal kit (depending on frame size). When catalog number starts with a 3, it indicates a kit with three terminals in each kit. Catalog number beginning with a TA indicates one terminal.

Base Mounting Hardware

Base mounting hardware is included with a circuit breaker or molded case switch. (Included with breaker.) If required separately, order 66A2546G02.

Terminal Shields IP30

Location	Number of Poles	Catalog Number
Line or Load	2, 3	**FJTS3K**
	4	**FJTS4K**

Interphase Barriers

Number of Poles	Catalog Number
3	**FJIPBK** ③
4	**FJIPBK4** ③

Multiwire Connectors

Field-installed multiwire connectors for the load side (OFF) end terminals are used to distribute the load from the circuit breaker to multiple devices without the use of separate distribution terminal blocks.

Multiwire lug kits include terminal shield, mounting hardware, insulators and tin-plated aluminum connectors to replace three mechanical load lugs. UL listed as used on the load side (OFF) end.

JG-Frame Multiwire Connectors Ordering Information (Package of 3)

Maximum Amperes	Wires per Terminal	Wire Size Range AWG Cu	Kit Catalog Number
250	3	14–2	**3TA250FJ3**
250	6	14–6	**3TA250FJ6**

Notes

① Individually packed.
② Standard line and load.
③ Individually priced.

Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

JG-Frame Accessories

Description	Reference Page	Two- and Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neutral
Internal Accessories (Only one internal accessory per pole)								
Alarm lockout (Make/Break)	**V4-T2-109**	—	—	■	—	—	■	—
Auxiliary switch (1A, 1B)	**V4-T2-109**	—	—	■	—	—	■	—
Auxiliary switch (2A, 2B)	**V4-T2-109**	—	—	■	—	—	■	—
Auxiliary switch and alarm switch combination	**V4-T2-109**	—	—	■	—	—	■	—
Shunt trip—standard	**V4-T2-109**	■	—	—	■	—	—	—
Undervoltage release mechanism	**V4-T2-110**	■	—	—	■	—	—	—
External Accessories								
End cap kit	**V4-T2-41**	●	●	●	●	●	●	●
Control wire terminal kit	**V4-T2-41**	●	●	●	●	●	●	●
Rear fed terminals	**V4-T2-41**	●	●	●	●	●	●	●
Multiwire connectors	**V4-T2-41**	●	●	●	●	●	●	●
Base mounting hardware	**V4-T2-41**	●	●	●	●	●	●	●
Interphase barriers	**V4-T2-41**	●	●	●	●	●	●	●
Padlockable handle block	**V4-T2-107**	—	■	—	—	■	—	—
Padlockable handle lock hasp	**V4-T2-107**	❑	—	❑	❑	—	❑	—
Key interlock kit	**V4-T2-107**	❑	—	❑	❑	—	❑	—
Sliding bar interlock—requires two breakers	**V4-T2-107**	●	●	●	—	—	—	—
Electrical operator	**V4-T2-107**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-107**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-415**	●	●	●	●	●	●	●
Earth leakage/ground fault protector	**V4-T2-92**	●	●	●	●	●	●	●
Drawout cassette	**V4-T2-115**	●	●	●	●	●	●	●
Digitrip 310+ test kit	**V4-T2-36**	●	●	●	●	●	●	●
Ammeter/cause of trip display	**V4-T2-106**	●	●	●	●	●	●	●
Cause of trip LED module	**V4-T2-106**	●	●	●	●	●	●	●
Modifications (Refer to Eaton)								
Moisture fungus treatment	**V4-T2-105**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application, UL 489 supplement SA and SB	①	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Note

① Contact Eaton.

Technical Data and Specifications

UL 489/IEC 60947-2 Interrupting Capacity (Symmetrical Amperes) (kA) Ratings

Circuit Breaker Type	Number of Poles	Volts AC (50/60 Hz) 220–240 I_{cu}	220–240 I_{cs}	380–415 I_{cu}	380–415 I_{cs}	480	600	690 ② I_{cu}	690 ② I_{cs}	Volts DC ① 250 ②③
JGE250	2, 3, 4	65	65	25	25	25	18	12	6	10
JGS250	2, 3, 4	85	85	40	40	35	18	12	6	22
JGH250	2, 3, 4	100	100	70	70	65	25	14	7	22
JGC250 ④	3, 4	200	200	100	100	100	35	16	12	42
JGU250 ④	3, 4	200	200	150	150	150	50	18	14	50
JGX250 ④	3, 4	200	200	200	200	200	50	18	14	50

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
JGC	240 V/200 kA	45.1	1.820
JGC	480 V/100 kA	45.1	1.820
JGC	600 V/35 kA	32.8	2.140
JGU	240 V/200 kA	45.1	1.820
JGU	480 V/150 kA	45.1	1.820
JGU	600 V/50 kA	32.8	2.140
JGX	240 V/200 kA	45.1	1.820
JGX	480 V/200 kA	45.1	1.820
JGX	600 V/50 kA	32.8	2.140

JG 310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	JG
Frames available	50 A, 100 A, 160 A 250 A
Continuous current range (A)	20–250A
Ground fault pickup (A)	10–250A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100, 150, 200
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG
Arcflash reduction maintenance system (or maintenance mode)	No
Interchangeable trip unit	Yes
High load alarm (suffix B20) ⑤	Yes
Ground fault alarm with trip (suffix B21) ⑤	Yes
Ground fault alarm, no trip (suffix B22) ⑤	Yes
Zone selective interlocking (suffix ZG)	LSI, LSIG
Cause of trip indication	Yes
Thru-cover accessories	Yes

Notes

① DC ratings apply to substantially non-inductive circuits.
② Two-pole circuit breaker, or two poles of three-pole circuit breaker.
③ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at 22 kA.
④ Current limiting per UL 489.
⑤ B2x suffixes cannot be combined with B2x suffixes.

JG 310+ Adjustability Specifications

310+ Settings		JG Frame 50 A	100 A	160 A	250 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r				
	A	20	40	63	100
	B	20	45	80	125
	C	25	50	90	150
	D	30	63	100	160
	E	32	70	110	175
	F	40	80	125	200
	G	45	90	150	225
	H (= I_n)	50	100	160	250
t_r = long delay time (seconds) (All 310+)	Position 1	2	2	2	2
	Position 2	4	4	4	4
	Position 3	7	7	7	7
	Position 4	10	10	10	10
	Position 5	12	12	12	12
	Position 6	15	15	15	15
	Position 7	20	20	20	20
	Position 8	24	24	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x	2x	2x	2x
	Position 2	3x	3x	3x	3x
	Position 3	4x	4x	4x	4x
	Position 4	5x	5x	5x	5x
	Position 5	6x	6x	6x	6x
	Position 6	7x	7x	7x	7x
	Position 7	8x	8x	8x	8x
	Position 8	10x	10x	10x	10x
	Position 9	14x	14x	14x	14x
t_{sd} = short delay time I^2t (milliseconds) (LS, LSG)	Fixed	67 at10x	67 at10x	67 at10x	67 at10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG)	Position 1	Inst	Inst	Inst	Inst
	Position 2	120	120	120	120
	Position 3	300	300	300	300
I_g = gound fault pickup (amperes) (LSG, LSIG)	Position 1	10	20	32	50
	Position 2	15	30	48	75
	Position 3	20	40	64	100
	Position 4	30	60	96	150
	Position 5	40	80	128	200
	Position 6	50	100	160	250
t_g = ground fault delay time (milliseconds) (LSG, LSIG)	Position 1	Inst	Inst	Inst	Inst
	Position 2	120	120	120	120
	Position 3	300	300	300	300
Independently Adjustable Instantaneous (I_i) setting ①	N/A				
Maintenance Mode pickup (2.5 x I_n) (amperes) ②	N/A				

Notes

① Not available for JG. Independently adjustable Ii setting available in LG, NG and RG ALSI and ALSIG trip units.

② Maintenance Mode not available for JG frames. It is available for KD, LD, MDL, LG, NG, and RG.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

JG-Frame

Number of Poles	Width	Height	Depth
2, 3	4.13 (104.9)	7.00 (177.8)	3.57 (90.7)
4	5.34 (135.6)	7.00 (177.8)	3.57 (90.7)

JG-Frame



Approximate Shipping Weight in Lbs (kg)

JG-Frame

Breaker Type	Number of Poles 2, 3	4
JGC	6.00 (2.70)	8.00 (3.60)
JGE	6.00 (2.70)	8.00 (3.60)
JGH	6.00 (2.70)	8.00 (3.60)
JGS	6.00 (2.70)	8.00 (3.60)
JGU	6.00 (2.70)	8.00 (3.60)
JGX	6.00 (2.70)	8.00 (3.60)

2

JG-Frame With Earth Leakage Module



LG-Frame (250–630 Amperes)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	
Catalog Number Selection	**V4-T2-48**
Product Selection	**V4-T2-49**
Accessories	**V4-T2-60**
Technical Data and Specifications	**V4-T2-61**
Dimensions and Weights	**V4-T2-63**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

LG-Frame (250–630 Amperes)

Product Description

LG breaker is HACR rated.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

2

Series G—LG-Frame (250–630 Amperes)

L G S 3 600 FA G C

Frame

L

Standard/Application

G = IEC/CE/UL/CSA

Performance

	600	480	415	240
E	18	35	35	65
S	25	50	50	85
H	35	65	70	100
C	50	100	100	200
U	65	150	150	200
X	65	200	200	200
K	Molded case switch			

Number of Poles

3 = Three
4 = Four—Neutral 0% protected
6 = Four—Neutral 60% protected
7 = Four—Neutral 100% protected
8 = Four—Neutral 0–60% protected
9 = Four—Neutral 0–100 protected

Amperes

250
300
350
400
500
600
630

Trip Unit

AA = Adj. adj.
FA = Fixed adj.
KS = Molded case switch
33 = 310+ electronic LS
32 = 310+ electronic LSI
35 = 310+ electronic LSG
36 = 310+ electronic LSIG
38 = 310+ electronic ALSI
39 = 310+ electronic ALSIG
NN = Frame only (630 A only; no trip unit)

Terminations/Hardware

Terminals	Mounting Hardware
M = Metric end caps	Metric
E = Imperial end caps	Imperial
G = Line/load standard	Metric
W = Without terminals	

Rating

Blank = 80% rated
C = 100% rated (for LGE, LGS and LGH only)

Trip Unit

LT 3 600 FA B20

Trip

LT

Number of Poles

3 = Three
4 = Four—neutral 0% protected
8 = Four—neutral 0/60% protected
9 = Four—neutral 0/100% protected

Amperes

250
300
350
400
500
600
630

Trip Unit

AA = Adj. adj., thermal-magnetic
FA = Fixed adj., thermal-magnetic
KS = Molded case switch
33 = 310+ electronic LS
32 = 310+ electronic LSI
35 = 310+ electronic LSG
36 = 310+ electronic LSIG
38 = 310+ electronic ALSI
39 = 310+ electronic ALSIG

Features (ETU Only) ①②

Blank= No feature
B20 = High load alarm
B21 = Ground fault alarm, with trip
B22 = Ground fault alarm, no trip
ZG = Zone selective interlocking

Notes

① Bxx features cannot be combined with other Bxx features.
② B21 and B22 available with LSG and LSIG trip units.

Product Selection

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware)

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA)
IC Rating: 35 kAIC at 415 and 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGE3250FAG	LGE3250AAG	LGE4250FAG	LGE4250AAG
300	LGE3300FAG	—	LGE4300FAG	—
320	—	LGE3320AAG	—	LGE4320AAG
350	LGE3350FAG	—	LGE4350FAG	—
400	LGE3400FAG	LGE3400AAG	LGE4400FAG	LGE4400AAG
500	LGE3500FAG	LGE3500AAG	LGE4500FAG	LGE4500AAG
600	LGE3600FAG	—	LGE4600FAG	—
630 ④	—	LGE3630AAG	—	LGE4630AAG

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA)
IC Rating: 50 kAIC at 415 and 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGS3250FAG	LGS3250AAG	LGS4250FAG	LGS4250AAG
300	LGS3300FAG	—	LGS4300FAG	—
320	—	LGS3320AAG	—	LGS4320AAG
350	LGS3350FAG	—	LGS4350FAG	—
400	LGS3400FAG	LGS3400AAG	LGS4400FAG	LGS4400AAG
500	LGS3500FAG	LGS3500AAG	LGS4500FAG	LGS4500AAG
600	LGS3600FAG	—	LGS4600FAG	—
630 ④	—	LGS3630AAG	—	LGS4630AAG

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA)
IC Rating: 70 kAIC at 415, 65 kAIC at 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGH3250FAG	LGH3250AAG	LGH4250FAG	LGH4250AAG
300	LGH3300FAG	—	LGH4300FAG	—
320	—	LGH3320AAG	—	LGH4320AAG
350	LGH3350FAG	—	LGH4350FAG	—
400	LGH3400FAG	LGH3400AAG	LGH4400FAG	LGH4400AAG
500	LGH3500FAG	LGH3500AAG	LGH4500FAG	LGH4500AAG
600	LGH3600FAG	—	LGH4600FAG	—
630 ④	—	LGH3630AAG	—	LGH4630AAG

Notes

① Replace suffix "G" with "W" for no line and load terminals.
② For two-pole applications, use two outer poles.
③ Neutral protection is indicated by the fourth character: 4 = 0%, 7 = 100%, 8 = adjustable 0–60% and 9 = 0–100%. Neutral is on LH side.
④ 320/630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA rating for the LG.
⑤ Adjustable thermal units are typically used in IEC markets and are not UL or CSA listed.

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware)

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA), Current Limiting Per UL 489
IC Rating: 100 kAIC at 415 and 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGC3250FAG	LGC3250AAG	LGC4250FAG	LGC4250AAG
300	LGC3300FAG	—	LGC4300FAG	—
320	—	LGC3320AAG	—	LGC4320AAG
350	LGC3350FAG	—	LGC4350FAG	—
400	LGC3400FAG	LGC3400AAG	LGC4400FAG	LGC4400AAG
500	LGC3500FAG	LGC3500AAG	LGC4500FAG	LGC4500AAG
600	LGC3600FAG	—	LGC4600FAG	—
630 ④	—	LGC3630AAG	—	LGC4630AAG

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA), Current Limiting Per UL 489
IC Rating: 150 kAIC at 415 and 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGU3250FAG	LGU3250AAG	LGU4250FAG	LGU4250AAG
300	LGU3300FAG	—	LGU4300FAG	—
320	—	LGU3320AAG	—	LGU4320AAG
350	LGU3350FAG	—	LGU4350FAG	—
400	LGU3400FAG	LGU3400AAG	LGU4400FAG	LGU4400AAG
500	LGU3500FAG	LGU3500AAG	LGU4500FAG	LGU4500AAG
600	LGU3600FAG	—	LGU4600FAG	—
630 ④	—	LGU3630AAG	—	LGU4630AAG

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA), Current Limiting Per UL 489
IC Rating: 200 kAIC at 415 and 480 Vac ①

	Three-Pole ②		Four-Pole (0%) ③	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic ④⑤
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LGX3250FAG	LGX3250AAG	LGX4250FAG	LGX4250AAG
300	LGX3300FAG	—	LGX4300FAG	—
320	—	LGX3320AAG	—	LGX4320AAG
350	LGX3350FAG	—	LGX4350FAG	—
400	LGX3400FAG	LGX3400AAG	LGX4400FAG	LGX4400AAG
500	LGX3500FAG	LGX3500AAG	LGX4500FAG	LGX4500AAG
600	LGX3600FAG	—	LGX4600FAG	—
630 ④	—	LGX3630AAG	—	LGX4630AAG

Notes

① Replace suffix "G" with "W" for no line and load terminals.
② For two-pole applications, use two outer poles.
③ Neutral protection is indicated by the fourth character: 4 = 0%, 7 = 100%, 8 = adjustable 0–60% and 9 = 0–100%. Neutral is on LH side.
④ 320/630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA rating for the LG.
⑤ Adjustable thermal units are typically used in IEC markets and are not UL or CSA listed.

Molded Case Switches [1]

Ampere Rating	Number of Poles	Catalog Number
400	3 [2]	LGK3400KSG
	4	LGK4400KSG
630 [3]	3 [2]	LGK3630KSG
	4	LGK4630KSG

Frame—IC Rating at 415/480 Volts

Maximum Amperes [3]	Three-Pole [2] Catalog Number	Four-Pole 0% Catalog Number
35/35		
630 [3]	LGE3630NN	LGE4630NN
	LGE3630NNWC	—
50/50		
630 [3]	LGS3630NN	LGS4630NN
	LGS3630NNWC	—
70/53		
630 [3]	LGH3630NN	LGH4630NN
	LGH3630NNWC	—
100/100 Current Limiting Per UL 489		
630	LGC3630NN	LGC4630NN
150/150 Current Limiting Per UL 489		
630	LGU3630NN	LGU4630NN
200/200 Current Limiting		
630	LGX3630NN	LGX4630NN

Thermal-Magnetic Trip Unit

	Three-Pole [2]		Four-Pole (0%) [5]	
	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic [4]	Fixed Thermal, Adjustable Magnetic	Adjustable Thermal, Adjustable Magnetic [4]
Ampere Rating	Catalog Number	Catalog Number	Catalog Number	Catalog Number
250	LT3250FA	LT3250AA	LT4250FA	LT4250AA
300	LT3300FA	—	LT4300FA	—
320	—	LT3320AA	—	LT4320AA
350	LT3350FA	—	LT4350FA	—
400	LT3400FA	LT3400AA	LT4400FA	LT4400AA
500	LT3500FA	LT3500AA	LT4500FA	LT4500AA
600	LT3600FA	—	LT4600FA	—
630	—	LT3630AA	—	LT4630AA

Notes

[1] Molded case switches will trip above 6300 amperes.
[2] For two-pole applications, use two outer poles.
[3] 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA rating for the LG.
[4] Adjustable thermal, adjustable magnetic trip units are typically used in IEC markets and are not UL or CSA listed.
[5] Neutral protection is indicated by the third character: 4 = 0%, 7 = 100%, 8 = adjustable 0–60% and 9 = 0–100%.
[6] 100% rated frame.

2

Digitrip 310+ Electronic Trip Units

See 310+ adjustability specifications on **Page V4-T2-62**.

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
Three-Pole					
250	**LT325033**	**LT325032**	**LT325035**	**LT325036**	**LGFCT250**
400	**LT340033**	**LT340032**	**LT340035**	**LT340036**	**LGFCT400**
600	**LT360033**	**LT360032**	**LT360035**	**LT360036**	**LGFCT600**
630 ②	**LT363033**	**LT363032**	**LT363035**	**LT363036**	**LGFCT600**
Four-Pole ③④					
250	**LT425033**	**LT425032**	**LT425035**	**LT425036**	—
400	**LT440033**	**LT440032**	**LT440035**	**LT440036**	—
600	**LT460033**	**LT460032**	**LT460035**	**LT460036**	—
630 ②	**LT463033**	**LT463032**	**LT463035**	**LT463036**	—

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V**
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor (630 A)	**LGFCT630**
External neutral sensor (600 A)	**LGFCT600**
External neutral sensor (400 A)	**LGFCT400**
External neutral sensor (250 A)	**LGFCT250**
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06**

Notes

① Required for four-wire systems if neutral protection is desired.
② 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA listed rating for the LG.
③ Neutral protection: 4= 0%, 6 = 60%, 7 = 100%. Electronic trip unit neutral protection is not adjustable.
④ Four-pole LSG and LSIG trip units are only available with 0% neutral protection.

IC Rating at 415/480 V
Complete LG Breakers with Electronic Trip Unit (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware) ①

See 310+ adjustability specifications on **Page V4-T2-62**.

IC Rating: 35 kAIC at 415 and 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGE325033G**	**LGE325032G**	**LGE325035G**	**LGE325036G**	**LGFCT250**
400	**LGE340033G**	**LGE340032G**	**LGE340035G**	**LGE340036G**	**LGFCT400**
600	**LGE360033G**	**LGE360032G**	**LGE360035G**	**LGE360036G**	**LGFCT600**
630 ④	**LGE363033G**	**LGE363032G**	**LGE363035G**	**LGE363036G**	**LGFCT600**
Four-Pole ⑤					
250	**LGE425033G**	**LGE425032G**	**LGE425035G**	**LGE425036G**	—
400	**LGE440033G**	**LGE440032G**	**LGE440035G**	**LGE440036G**	—
600	**LGE460033G**	**LGE460032G**	**LGE460035G**	**LGE460036G**	—
630 ④	**LGE463033G**	**LGE463032G**	**LGE463035G**	**LGE463036G**	—

IC Rating: 50 kAIC at 415 and 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGS325033G**	**LGS325032G**	**LGS325035G**	**LGS325036G**	**LGFCT250**
400	**LGS340033G**	**LGS340032G**	**LGS340035G**	**LGS340036G**	**LGFCT400**
600	**LGS360033G**	**LGS360032G**	**LGS360035G**	**LGS360036G**	**LGFCT600**
630 ④	**LGS363033G**	**LGS363032G**	**LGS363035G**	**LGS363036G**	**LGFCT600**
Four-Pole ⑤⑥					
250	**LGS425033G**	**LGS425032G**	**LGS425035G**	**LGS425036G**	—
400	**LGS440033G**	**LGS440032G**	**LGS440035G**	**LGS440036G**	—
600	**LGS460033G**	**LGS460032G**	**LGS460035G**	**LGS460036G**	—
630 ④	**LGS463033G**	**LGS463032G**	**LGS463035G**	**LGS463036G**	—

IC Rating: 70 kAIC at 415 Vac, 65 kAIC at 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGH325033G**	**LGH325032G**	**LGH325035G**	**LGH325036G**	**LGFCT250**
400	**LGH340033G**	**LGH340032G**	**LGH340035G**	**LGH340036G**	**LGFCT400**
600	**LGH360033G**	**LGH360032G**	**LGH360035G**	**LGH360036G**	**LGFCT600**
630 ④	**LGH363033G**	**LGH363032G**	**LGH363035G**	**LGH363036G**	**LGFCT600**
Four-Pole ⑤⑥					
250	**LGH425033G**	**LGH425032G**	**LGH425035G**	**LGH425036G**	—
400	**LGH440033G**	**LGH440032G**	**LGH440035G**	**LGH440036G**	—
600	**LGH460033G**	**LGH460032G**	**LGH460035G**	**LGH460036G**	—
630 ④	**LGH463033G**	**LGH463032G**	**LGH463035G**	**LGH463036G**	—

Notes

① Replace suffix "G" with "W" for no line and load terminals.
② Required for four-wire systems if neutral protection is desired.
③ For two-pole applications, use two outer poles.
④ 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA listed rating for the LG.
⑤ Neutral protection: 4= 0%, 6 = 60%, 7 = 100%. Electronic trip unit neutral protection is not adjustable.
⑥ Four-pole breakers with LSG and LSIG trip units are only available with 0% neutral protection.

IC Rating at 415/480 V
Complete LG Breakers with Electronic Trip Unit (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware) ①

2

See 310+ adjustability specifications on **Page V4-T2-62**.

IC Rating: 100 kAIC at 415 Vac and 480 Vac, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGC325033G**	**LGC325032G**	**LGC325035G**	**LGC325036G**	**LGFCT250**
400	**LGC340033G**	**LGC340032G**	**LGC340035G**	**LGC340036G**	**LGFCT400**
600	**LGC360033G**	**LGC360032G**	**LGC360035G**	**LGC360036G**	**LGFCT600**
630 ④	**LGC363033G**	**LGC363032G**	**LGC363035G**	**LGC363036G**	**LGFCT600**
Four-Pole ⑤⑥					
250	**LGC425033G**	**LGC425032G**	**LGC425035G**	**LGC425036G**	—
400	**LGC440033G**	**LGC440032G**	**LGC440035G**	**LGC440036G**	—
600	**LGC460033G**	**LGC460032G**	**LGC460035G**	**LGC460036G**	—
630 ④	**LGC463033G**	**LGC463032G**	**LGC463035G**	**LGC463036G**	—

IC Rating: 150 kAIC at 415 Vac and 480 Vac, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGU325033G**	**LGU325032G**	**LGU325035G**	**LGU325036G**	**LGFCT250**
400	**LGU340033G**	**LGU340032G**	**LGU340035G**	**LGU340036G**	**LGFCT400**
600	**LGU360033G**	**LGU360032G**	**LGU360035G**	**LGU360036G**	**LGFCT600**
630 ④	**LGU363033G**	**LGU363032G**	**LGU363035G**	**LGU363036G**	**LGFCT600**
Four-Pole ⑤					
250	**LGU425033G**	**LGU425032G**	**LGU425035G**	**LGU425036G**	—
400	**LGU440033G**	**LGU440032G**	**LGU440035G**	**LGU440036G**	—
600	**LGU460033G**	**LGU460032G**	**LGU460035G**	**LGU460036G**	—
630 ④	**LGU463033G**	**LGU463032G**	**LGU463035G**	**LGU463036G**	—

IC Rating: 200 kAIC at 415 Vac and 480 Vac, Current Limiting Per UL 489

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ② Catalog Number
Three-Pole ③					
250	**LGX325033G**	**LGX325032G**	**LGX325035G**	**LGX325036G**	**LGFCT250**
400	**LGX340033G**	**LGX340032G**	**LGX340035G**	**LGX340036G**	**LGFCT400**
600	**LGX360033G**	**LGX360032G**	**LGX360035G**	**LGX360036G**	**LGFCT600**
630 ④	**LGX363033G**	**LGX363032G**	**LGX363035G**	**LGX363036G**	**LGFCT600**
Four-Pole ⑤					
250	**LGX425033G**	**LGX425032G**	**LGX425035G**	**LGX425036G**	—
400	**LGX440033G**	**LGX440032G**	**LGX440035G**	**LGX440036G**	—
600	**LGX460033G**	**LGX460032G**	**LGX460035G**	**LGX460036G**	—
630 ④	**LGX463033G**	**LGX463032G**	**LGX463035G**	**LGX463036G**	—

Notes

① Replace suffix "G" with "W" for no line and load terminals.
② Required for four-wire systems if neutral protection is desired.
③ For two-pole applications, use two outer poles.
④ 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA listed rating for the LG.
⑤ Neutral protection: 4= 0%, 6 = 60%, 7 = 100%. Electronic trip unit neutral protection is not adjustable.
⑥ Four-pole breakers with LSG and LSIG trip units are only available with 0% neutral protection.

LG 100% Rated Circuit Breaker—Thermal-Magnetic Trip Unit

Complete Breaker (Includes Frame, Trip Unit, Standard Terminals and Mounting Hardware)

LG-Frame

LG-Frame—630 Amperes (600 Amperes UL, CSA) IC Rating: 35 kAIC at 415 and 480 Vac ①

	Three-Pole ② Fixed Thermal, Adjustable Magnetic
Ampere Rating	**Catalog Number**
250	**LGE3250FAGC**
300	**LGE3300FAGC**
320	—
350	**LGE3350FAGC**
400	**LGE3400FAGC**
500	**LGE3500FAGC**
600	**LGE3600FAGC**
630 ④	—

LG-Frame—630 Amperes (600 Amperes UL, CSA) IC Rating: 50 kAIC at 415 and 480 Vac ①

	Three-Pole ② Fixed Thermal, Adjustable Magnetic
Ampere Rating	**Catalog Number**
250	**LGS3250FAGC**
300	**LGS3300FAGC**
320	—
350	**LGS3350FAGC**
400	**LGS3400FAGC**
500	**LGS3500FAGC**
600	**LGS3600FAGC**
630 ④	—

LG-Frame—630 Amperes (600 Amperes UL, CSA) IC Rating: 70 kAIC at 415, 65 kAIC at 480 Vac ①

	Three-Pole ② Fixed Thermal, Adjustable Magnetic
Ampere Rating	**Catalog Number**
250	**LGH3250FAGC**
300	**LGH3300FAGC**
320	—
350	**LGH3350FAGC**
400	**LGH3400FAGC**
500	**LGH3500FAGC**
600	**LGH3600FAGC**
630 ④	—

Notes

① Replace suffix "G" with "W" for no line and load terminals.
② For two-pole applications, use two outer poles.

LG 100% Rated Electronic Breaker Per UL 489

See 310+ adjustability specifications on **Page V4-T2-62**.

IEC/UL/CSA 35 kAIC at 415 and 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
250	**LGE325033GC**	**LGE325032GC**	**LGE325035GC**	**LGE325036GC**	**LGFCT250**
400	**LGE340033GC**	**LGE340032GC**	**LGE340035GC**	**LGE340036GC**	**LGFCT400**
600	**LGE360033GC**	**LGE360032GC**	**LGE360035GC**	**LGE360036GC**	**LGFCT600**
630 ②	**LGE363033GC**	**LGE363032GC**	**LGE363035GC**	**LGE363036GC**	**LGFCT600**

IEC/UL/CSA 50 kAIC at 415 and 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
250	**LGS325033GC**	**LGS325032GC**	**LGS325035GC**	**LGS325036GC**	**LGFCT250**
400	**LGS340033GC**	**LGS340032GC**	**LGS340035GC**	**LGS340036GC**	**LGFCT400**
600	**LGS360033GC**	**LGS360032GC**	**LGS360035GC**	**LGS360036GC**	**LGFCT600**
630 ②	**LGS363033GC**	**LGS363032GC**	**LGS363035GC**	**LGS363036GC**	**LGFCT600**

IEC/UL/CSA 70 kAIC at 415 and 480 Vac

Ampere Rating	LS Catalog Number	LSI Catalog Number	LSG Catalog Number	LSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
250	**LGH325033GC**	**LGH325032GC**	**LGH325035GC**	**LGH325036GC**	**LGFCT250**
400	**LGH340033GC**	**LGH340032GC**	**LGH340035GC**	**LGH340036GC**	**LGFCT400**
600	**LGH360033GC**	**LGH360032GC**	**LGH360035GC**	**LGH360036GC**	**LGFCT600**
630 ②	**LGH363033GC**	**LGH363032GC**	**LGH363035GC**	**LGH363036GC**	**LGFCT600**

Notes

① Required for four-wire systems if neutral protection is required.

② 630 amperes is not a UL or CSA listed rating. 600 amperes is the maximum UL and CSA listed rating for the LG.

LG Electronic Breaker with Arcflash Reduction Maintenance System

See 310+ adjustability specifications on **Page V4-T2-62**.

Series G LG circuit breakers are available with the Arcflash Reduction Maintenance System™ integrated into the electronic trip units helping to improve safety by providing a simple and reliable method to reduce fault clearing time. The Arcflash Reduction Maintenance System unit utilizes a separate analog trip circuit that provides faster interruption times than the standard (digital) "instantaneous" protection. Work locations downstream of a circuit breaker with an Arcflash Reduction Maintenance System unit can have a significantly lower incident energy level, reducing arc flash potential to the system.

LG with Arcflash Reduction Maintenance System

LG Electronic Breaker with Arcflash Reduction Maintenance System

Ampere Rating	ALSI Catalog Number	ALSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
IEC/UL/CSA 35 kAIC at 415 and 480 Vac			
250	**LGE325038G**	**LGE365039G**	**LGFCT250**
400	**LGE340038G**	**LGE340039G**	**LGFCT400**
600	**LGE360038G**	**LGE360039G**	**LGFCT600**
630	**LGE363038G**	**LGE363039G**	**LGFCT600**
IEC/UL/CSA 50 kAIC at 415 and 480 Vac			
250	**LGS325038G**	**LGS365039G**	**LGFCT250**
400	**LGS340038G**	**LGS340039G**	**LGFCT400**
600	**LGS360038G**	**LGS360039G**	**LGFCT600**
630	**LGS363038G**	**LGS363039G**	**LGFCT600**
IEC/UL/CSA 70 kAIC at 415 and 480 Vac			
250	**LGH325038G**	**LGH365039G**	**LGFCT250**
400	**LGH340038G**	**LGH340039G**	**LGFCT400**
600	**LGH360038G**	**LGH360039G**	**LGFCT600**
630	**LGH363038G**	**LGH363039G**	**LGFCT600**
IEC/UL/CSA 100 kAIC at 415 and 480 Vac, Current Limiting Per UL 489			
250	**LGC325038G**	**LGC365039G**	**LGFCT250**
400	**LGC340038G**	**LGC340039G**	**LGFCT400**
600	**LGC360038G**	**LGC360039G**	**LGFCT600**
630	**LGC363038G**	**LGC363039G**	**LGFCT600**
IEC/UL/CSA 150 kAIC at 415 and 480 Vac, Current Limiting Per UL 489			
250	**LGU325038G**	**LGU365039G**	**LGFCT250**
400	**LGU340038G**	**LGU340039G**	**LGFCT400**
600	**LGU360038G**	**LGU360039G**	**LGFCT600**
630	**LGU363038G**	**LGU363039G**	**LGFCT600**
IEC/UL/CSA 200 kAIC at 415 and 480 Vac, Current Limiting Per UL 489			
250	**LGX325038G**	**LGX365039G**	**LGFCT250**
400	**LGX340038G**	**LGX340039G**	**LGFCT400**
600	**LGX360038G**	**LGX360039G**	**LGFCT600**
630	**LGX363038G**	**LGX363039G**	**LGFCT600**

LG Electronic Trip Units with Arcflash Reduction Maintenance System

Ampere Rating	ALSI Catalog Number	ALSIG Catalog Number	Neutral CT for LSG and LSIG ① Catalog Number
250	**LT325038**	**LT325039**	**LGFCT250**
400	**LT340038**	**LT340039**	**LGFCT400**
600	**LT360038**	**LT360039**	**LGFCT600**
630	**LT363038**	**LT363039**	**LGFCT600**

Note

① Required for four-wire systems if neutral protection is required.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/ Number of Conductors	Metric Wire Range (mm^2)	Number of Terminals Included	Catalog Number
400	Aluminum	Cu/Al	500–750 (1)	240–380 (1)	3	**3TA631LK** ①
400	Aluminum	Cu/Al	500–750 (1)	240–380 (1)	4	**4TA631LK** ①
400	Copper	Cu	500–750 (1)	240–380 (1)	3	**3T631LK** ①
400	Copper	Cu	500–750 (1)	240–380 (1)	4	**4T631LK** ①
630	Aluminum	Cu/Al	2–500 (2)	35–240 (2)	1	**TA632L**
630	Aluminum	Cu/Al	2–500 (2)	35–240 (2)	3	**3TA632LK** ①②
630	Aluminum	Cu/Al	2–500 (2)	35–240 (2)	4	**4TA632LK** ①②
630	Copper	Cu	2–500 (2)	35–240 (2)	3	**3T632LK** ①
630	Copper	Cu	2–500 (2)	35–240 (2)	4	**4T632LK** ①
400	Aluminum	Cu/Al	3–500 (1)	35–240 (1)	1	**TA350LK** ②
400	Copper	Cu	3–500 (1)	35–240 (1)	1	**T350LK**

Base Mounting Hardware

Base mounting hardware is included with a circuit breaker or molded case switch. (Included with breaker.) If required separately, order 66A4560G03.

Terminal Covers

Description	Catalog Number
Three-pole terminal cover ③	**LTS3K**
Four-pole terminal cover ③	**LTS4K**

End Cap Kits (MIO Metric Nuts)

Number of Poles	Catalog Number
3	**L3RTWK**
4	**L4RTWK**

Control Wire Terminal Kit

Description	Terminal Body Type	Catalog Number
Three-pole kit	Aluminum	**3TA632LKW**
Four-pole kit	Aluminum	**4TA632LKW**
Three-pole kit	Copper	**3T632LKW**
Four-pole kit	Copper	**4T632LKW**

Terminal Spreaders

Number of Poles	Catalog Number
3	**LGTEW3**
4	**LGTEW4**

Terminal Extensions

Number of Poles	Catalog Number
3	**LGTES3**
4	**LGTES4**

Handle Extension

Description	Catalog Number
Handle extension	**HEXLG**

Interphase Barrier

Package of 2	Catalog Number
Interphase barrier	**IPB3**

Rear Fed Terminals

Maximum Amperes	Wire Size Range AWG Cu	Catalog Number
400	2–500 kcmil	**TA350LKRF**
400	2–500 kcmil	**3TA350LKRF**
630	2–500 (2) kcmil	**TA632LKRF**
630	2–500 (2) kcmil	**3TA632LKRF**

Rear fed terminals allow the cable to connect to the breaker from the back instead of the top. Terminal shields or interphase barriers are included with each rear fed terminal kit (depending on frame size). When catalog number starts with a 3, it indicates a kit with three terminals in each kit. Catalog number beginning with a TA indicates one terminal.

Multiwire Connectors

Field-installed multiwire connectors for the load side (OFF) end terminals are used to distribute the load from the circuit breaker to multiple devices without the use of separate distribution terminal blocks.

Multiwire lug kits include terminal shield, mounting hardware, insulators and tin-plated aluminum connectors to replace three mechanical load lugs. UL listed as used on the load side (OFF) end.

LG-Frame Multiwire Connectors Ordering Information (Package of 3)

Maximum Amperes	Wires per Terminal	Wire Size Range AWG Cu	Kit Catalog Number
600	6	14–1/0	**3TA600L6K**

Notes

① Includes LTS3K (three-pole) or LTS4K (four-pole) terminal covers.
② Standard terminal included with complete breaker.
③ Included in TA63IL, T63IL, TA632L kits listed above.

StrandAble Multiwire Terminals

Field-installed multiwire terminals are UL listed for nearly any class of rigid- or fine-strand wire without the use of additional fittings. Used on the load side of the circuit breaker to distribute the load to multiple devices without the use of a power distribution block.

StrandAble multiwire terminals are available in three-pole kits that include the necessary hardware and shielding.

LG Frame StrandAble Multiwire Terminal

LG Frame StrandAble Multiwire Terminals (Three-Pole Kits)

Maximum Amperage	Wire Class	Wire Range	Shield Included	Kit Catalog Number
600	B & C	(6) 12–2/0	Interphase barrier	**3TA600L6SWKI**
	D, G, H, I, K, M	(6) 8–1/0		
	B & C	(6) 12–2/0	Terminal shield	**3TA600L6SWKS**
	D, G, H, I, K, M	(6) 8–1/0		

Terminals and Terminal Cover for the LG Breaker— Includes LTS3K (Three-Pole) or LTS4K (Four-Pole) Terminal Covers

Note: Extended terminal covers add 2.13 inches (54.0 mm) to breaker length.



Accessories

Base Mounting Hardware

Base mounting hardware is included with a circuit breaker or molded case switch. (Included with breaker.) If required separately, order 66A4560G03.

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

LG-Frame Accessories

Description	Reference Page	Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neu.
Internal Accessories (Only One Internal Accessory Per Pole)								
Alarm lockout (Make/Break)	**V4-T2-109**			■			■	
Auxiliary switch (1A, 1B)	**V4-T2-109**			■			■	
Auxiliary switch (2A, 2B)	**V4-T2-109**			■			■	
Auxiliary switch and alarm switch combination	**V4-T2-109**			■			■	
Shunt trip—standard	**V4-T2-109**	■			■			
Undervoltage release mechanism	**V4-T2-110**	■			■			
External Accessories								
End cap kit	**V4-T2-58**	●			●			
Handle extension	**V4-T2-58**	●			●			
Terminal cover	**V4-T2-58**	●			●			
Rear fed terminals	**V4-T2-58**	●	●	●	●	●	●	●
Multiwire connectors	**V4-T2-58**	●	●	●	●	●	●	●
Padlockable handle block	**V4-T2-107**		■			■		
Padlockable handle lock hasp	**V4-T2-107**	❑		❑	❑		❑	
Key interlock kit	**V4-T2-107**	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-107**	●	●	●	●	●	●	●
Electrical operator	**V4-T2-107**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-107**	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-107**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-415**	●	●	●	●	●	●	●
Earth leakage/ground fault protector	**V4-T2-92**	●	●	●	●	●	●	●
Drawout cassette	**V4-T2-115**	●	●	●	●	●	●	●
Digitrip 310+ test kit	**V4-T2-52**	●	●	●	●	●	●	●
Ammeter/cause of trip display	**V4-T2-106**	●	●	●	●	●	●	●
Cause of trip LED module	**V4-T2-106**	●	●	●	●	●	●	●
Modifications (Refer to Eaton)								
Moisture fungus treatment	**V4-T2-105**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application, UL 489 Supplement SA and SB	①	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Note

① Contact Eaton.

Technical Data and Specifications

Interrupting Capacity Ratings

UL 489/IEC 60947-2 Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA rms Symmetrical Amperes) (kA) Volts AC (50/60 Hz) 240–240 Icu	Ics	380–415 Icu	Ics	480	600	690 Icu	Ics	Volts DC ① 250 ②③ Icu	Ics
LGE630	3, 4	65	65	35	35	35	18	12	6	22	22
LGS630	3, 4	85	85	50	50	50	25	20	10	22	22
LGH630	3, 4	100	100	70	70	65	35	25	13	42	42
LGC630 ④	3, 4	200	200	100	100	100	50	30	15	42	42
LGU630 ④	3, 4	200	200	150	150	150	65	35	18	50	50
LGX630 ④	3, 4	200 ⑤	200	200	200	200	65	35	18	50	50

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
LGC	240 V/200 kA	56.4	5.873
LGC	480 V/100 kA	56.4	5.873
LGC	600 V/50 kA	56.4	6.690
LGU	240 V/200 kA	77.7	7.320
LGU	480 V/150 kA	77.7	7.320
LGU	600 V/65 kA	50.6	6.690
LGX	240 V/200 kA	77.7	7.320
LGX	480 V/200 kA	77.7	7.320
LGX	600 V/65 kA	50.6	6.690

LG 310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	LG
Frames available	250 A, 400 A, 600 A
Continuous current range (A)	100–600 A
Ground fault pickup (A)	50–600 A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100, 150, 200
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash reduction maintenance system (or maintenance mode)	Yes
Interchangeable trip unit	Yes
High load alarm (suffix B20) ⑤	Yes
Ground fault alarm with trip (suffix B21) ⑤	Yes
Ground fault alarm, no trip (suffix B22) ⑤	Yes
Zone selective interlocking (suffix ZG)	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes
Thru-cover accessories	Yes

Notes

① DC rating apply to substantially non-inductive circuits.
② Two-pole circuit breaker, or two poles of three-pole circuits.
③ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at–kA.
④ Current limiting per UL 489.
⑤ B2x suffixes cannot be combined with B2x suffixes.

LG 310+ Adjustability Specifications

310+ Settings		LG Frame 250 A	400 A	600 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r			
	A	100	160	250
	B	125	200	300
	C	150	225	315
	D	160	250	350
	E	175	300	400
	F	200	315	450
	G	225	350	500
	H (= I_n)	250	400	600
t_r = long delay time (seconds) (All 310+)	Position 1	2	2	2
	Position 2	4	4	4
	Position 3	7	7	7
	Position 4	10	10	10
	Position 5	12	12	12
	Position 6	15	15	15
	Position 7	20	20	20
	Position 8	24	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x	2x	2x
	Position 2	3x	3x	3x
	Position 3	4x	4x	4x
	Position 4	5x	5x	5x
	Position 5	6x	6x	6x
	Position 6	7x	7x	7x
	Position 7	8x	8x	8x
	Position 8	10x	10x	10x
	Position 9	12x	12x	12x
t_{sd} = short delay time I^2t (milliseconds) (LS, LSG)	Fixed	67 at10x	67 at10x	67 at10x
t_{sd} = short delay time flat (milliseconds) ① (LSI, LSIG, ALSI, ALSIG)	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
I_g = gound fault pickup (amperes) (LSG, LSIG, ALSIG)	Position 1	50	80	120
	Position 2	75	120	180
	Position 3	100	160	240
	Position 4	150	240	360
	Position 5	200	320	480
	Position 6	250	400	600
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
Independently Adjustable Instantaneous (I_i) setting (ALSI, ALSIG)	Yes	2.5x, 4x, 6x, 7x, 8x, 10x, 12x	2.5x, 4x, 6x, 7x, 8x, 10x, 12x	2.5x, 4x, 6x, 7x, 8x, 10x, 12x
Maintenance Mode (remote) pickup (2.5 x I_n) ② (ALSI, ALSIG)	Fixed	2.5x		

Notes

① 50 ms for ALSI and ALSIG trip units.

② Maintenance Mode is enabled remotely using a 24 Vdc circuit.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

LG-Frame

Number of Poles	Width	Height	Depth
2, 3	5.48 (139.2)	10.13 (257.3)	4.09 (103.9)
4	7.22 (183.4)	10.13 (257.3)	4.09 (103.9)

LG-Frame

Note: TA63IL, T63IL, T632L, TA632L terminals add 1.19 inches (30.2 mm) to line or load side of LG. LTS3K or LTS4K terminal covers add 2.13 inches (54.1 mm) to line or load side of LG.



Three-Pole

Approximate Shipping Weight in Lbs (kg)

LG-Frame

Breaker Type	Two- and Three-Pole	Four-Pole
LGE, LGS, LGH, LGC, LGU, LGX	16 (7.3)	20 (9.1)

Notes

① DC rating apply to substantially non-inductive circuits.
② Two-pole circuit breaker, or two poles of three-pole circuits.
③ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at–kA.
④ Three-poles in series. 750 Vdc ratings available (four-pole in series, not UL listed). Contact Eaton.
⑤ IEC rating is 300 kA at 240 Vac.
⑥ Current limiting per UL 489.

LG-Frame With Earth Leakage Module



NG-Frame (1200 Ampere)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	
Catalog Number Selection	**V4-T2-66**
Product Selection Guide and Ordering Information	**V4-T2-67**
Accessories	**V4-T2-70**
Technical Data and Specifications	**V4-T2-71**
Dimensions and Weights	**V4-T2-73**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

NG-Frame (320–1200 Amperes)

Product Description

- All Eaton NG-Frame circuit breakers are suitable for reverse feed use
- All NG-Frame circuit breakers are HACR rated

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

2

NG Circuit Breaker with 310+ Electronic Trip Unit

NG H 3 080 39 ZG E C

Frame
NG

Performance at 480 Vac
S = 50 kAIC
H = 65 kAIC
C = 100 kAIC
U = 150 kAIC ①
K = Molded case switch

Poles
2 = Two
3 = Three
4 = Four; neutral ② 0% protected
7 = Four; neutral ② 100% protected
9 = Four; neutral ② 0/60/100% adjustable protection

Amperes
080 = 800
120 = 1200

Trip Unit
33 = 310+ Electronic LS
32 = 310+ Electronic LSI
35 = 310+ Electronic LSG
36 = 310+ Electronic LSIG
38 = 310+ Electronic ALSI with maintenance mode
39 = 310+ Electronic ALSIG with maintenance mode
KS = Molded case switch

Feature
Blank = No feature
B20 = High load alarm
B21 = Ground fault alarm, with trip
B22 = Ground fault alarm, no trip
ZG = Zone selective interlocking

Terminations ③
M = Metric tapped line/load conductors
E = Imperial tapped line/load conductors

Rating
Blank = 80% rated
C = 100% rated

Notes

① 800 A only.
② Neutral inn left pole on GN; right pole on NG.
③ Breakers do not ship with lugs.

Trip units are factory installable only.

Product Selection Guide and Ordering Information

Type NGS Standard Interrupting Capacity—U_e Max. 690 Vac, 50 kA I_{cu} at 480 Vac or 415 Vac

See 310+ adjustability specifications on **Page V4-T2-72**.

Maximum Continuous Ampere Rating at 40 °C ①②	Number of Poles	Circuit Breaker Frame Including Digitrip Electronic Trip Unit with Imperial Tapped Conductors						
		LS	LSI	LSG	LSIG	ALSI	ALSIG	Neutral CT for LSG and LSIG ③
800	2	NGS208033E	NGS208032E	NGS208035E	NGS208036E	—	—	—
	3	NGS308033E	NGS308032E	NGS308035E	NGS308036E	NGS308038E	NGS308039E	NGFCT120
	4	NGS408033E	NGS408032E	NGS408035E ④	NGS408036E ④	NGS408038E	NGS408039E ④	—
	4 ⑤	NGS708033E	NGS708032E	—	—	NGS708038E	—	—
	4 ⑥	NGS908033E	NGS908032E	—	—	NGS908038E	—	—
1200 ⑥	2	NGS212033E	NGS212032E	NGS212035E	NGS212036E	—	—	—
	3	NGS312033E	NGS312032E	NGS312035E	NGS312036E	NGS312038E	NGS312039E	NGFCT120
	4	NGS412033E	NGS412032E	NGS412035E ④	NGS412036E ④	—	NGS412039E ④	—
	4 ⑤	NGS712033E	NGS712032E	—	—	NGS712038E	—	—
	4 ⑥	NGS912033E	NGS912032E	—	—	NGS912038E	—	—

Molded Case Switches ⑦⑧⑨⑩

	U_e Maximum 690 Vac			
Ampere Rating	Three-Pole	Catalog Number	Four-Pole	Catalog Number
800	MCS with Imperial line and load terminals	NGK3080KSE	MCS with Imperial line and load terminals	NGK4080KSE
1200	MCS with Imperial line and load terminals	NGK3120KSE	MCS with Imperial line and load terminals	NGK4120KSE
1250	MCS with Imperial line and load terminals	NGK3125KSE	MCS with Imperial line and load terminals	NGK43125KSE

Notes

① For AC use only.
② NG MCCBs are suitable for 40 °C or 50 °C applications. Order suffix V3 to eliminate standard 40 °C labeling.
③ Required for four-wire systems if neutral protection is desired. Sold separately.
④ Neutral 0% protected. NG, neutral in right pole; GN, neutral in left pole.
⑤ Neutral 100% protected (denoted by 7 in digit four); no neutral protection available with LSG or LSIG trip units.
⑥ Neutral 0%/60%/100% adjustable protection (denoted by 9 in digit four).
⑦ Non-UL listed NG 1250 with 1250 ampere trip unit is also available.
⑧ For AC use only. Molded case switch will trip above 14,000 amperes.
⑨ For two-pole applications, use outer poles of three-pole molded case switch.
⑩ Add "**M**" to above catalog numbers for metric tapped line/load conductors.

2

Type NGH High Interrupting Capacity—U_e Max. 690 Vac, 65 kA I_{cu} at 480 Vac or 415 Vac

See 310+ adjustability specifications on **Page V4-T2-72**.

Maximum Continuous Ampere Rating at 40 °C ①②	Number of Poles	Circuit Breaker Frame Including Digitrip Electronic Trip Unit						
		LS	LSI	LSG	LSIG	ALSI	ALSIG	Neutral CT for LSG and LSIG ③
800	2	NGH208033E	NGH208032E	NGH208035E	NGH208036E	—	—	—
	3	NGH308033E	NGH308032E	NGH308035E	NGH308036E	NGH308038E	NGH308039E	NGFCT120
	4	NGH408033E	NGH408032E	NGH408035E ④	NGH408036E ④	NGH408038E	NGH408039E ④	—
	4 ⑤	NGH708033E	NGH708032E	—	—	NGH708038E	—	—
	4 ⑥	NGH908033E	NGH908032E	—	—	NGH908038E	—	—
1200	2	NGH212033E	NGH212032E	NGH212035E	NGH212036E	—	—	—
	3	NGH312033E	NGH312032E	NGH312035E	NGH312036E	NGH312038E	NGH312039E	NGFCT120
	4	NGH412033E	NGH412032E	NGH412035E ④	NGH412036E ④	—	NGH412039E ④	—
	4 ⑤	NGH712033E	NGH712032E	—	—	NGH712038E	—	—
	4 ⑥	NGH912033E	NGH912032E	—	—	NGH912038E	—	—

Type NGC Very High Capacity—U_e Max. 690 Vac, 100 kA I_{cu} at 480 Vac or 415 Vac

See 310+ adjustability specifications on **Page V4-T2-72**.

Maximum Continuous Ampere Rating at 40 °C ①②	Number of Poles	Circuit Breaker Frame Including Digitrip Electronic Trip Unit						
		LS	LSI	LSG	LSIG	ALSI	ALSIG	Neutral CT for LSG and LSIG ③
800	2	NGC208033E	NGC208032E	NGC208035E	NGC208036E	—	—	—
	3	NGC308033E	NGC308032E	NGC308035E	NGC308036E	NGC308038E	NGC308039E	NGFCT120
	4	NGC408033E	NGC408032E	NGC408035E ④	NGC408036E ④	NGC408038E	NGC408039E ④	—
	4 ⑤	NGC708033E	NGC708032E	—	—	NGC708038E	—	—
	4 ⑥	NGC908033E	NGC908032E	—	—	NGC908038E	—	—
1200	2	NGC212033E	NGC212032E	NGC212035E	NGC212036E	—	—	—
	3	NGC312033E	NGC312032E	NGC312035E	NGC312036E	NGC312038E	NGC312039E	NGFCT120
	4	NGC412033E	NGC412032E	NGC412035E ④	NGC412036E ④	—	NGC412039E ④	—
	4 ⑤	NGC712033E	NGC712032E	—	—	NGC712038E	—	—
	4 ⑥	NGC912033E	NGC912032E	—	—	NGC912038E	—	—

Type NGU Ultra High Capacity—U_e Max. 600 Vac, 150 kA at 480 Vac

See 310+ adjustability specifications on **Page V4-T2-72**.

Maximum Continuous Ampere Rating at 40 °C ①②	Number of Poles	Circuit Breaker Frame Including Digitrip Electronic Trip Unit						
		LS	LSI	LSG	LSIG	ALSI	ALSIG	Neutral CT for LSG and LSIG ③
800	3	NGU308033E	NGU308032E	NGU308035E	NGU308036E	NGU308038E	NGU308039E	NGFCT120

Notes

① For AC use only.
② NG MCCBs are suitable for 40 °C or 50 °C applications. Order suffix V3 to eliminate standard 40 °C labeling.
③ Required for four-wire systems if neutral protection is desired. Sold separately.
④ Neutral 0% protected. NG, neutral in right pole; GN, neutral in left pole.
⑤ Neutral 100% protected (denoted by 7 in digit four); no neutral protection available with LSG or LSIG trip units.
⑥ Neutral 0%/60%/100% adjustable protection (denoted by 9 in digit four).

Accessories Selection Guide and Ordering Information

Line and Load Terminals

N-Frame circuit breakers do not include terminals as standard. When copper or Cu/Al terminals are required, order by catalog number.

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire (Number of Conductors)	AWG Wire Catalog Number ①	Metric Wire Range mm^2	Metric Catalog Number ①
Standard Cu/Al Pressure Terminals						
700	Aluminum	Cu/Al	1–500 (2)	**TA700NB1**	50–240	**TA700NB1M**
1000	Aluminum	Cu/Al	3/0–400 (3)	**TA1000NB1**	95–185	**TA1000NB1M**
1200	Aluminum	Cu/Al	4/0–500 (4)	**TA1200NB1**	120–240	**TA1200NB1M**
1200	Aluminum	Cu/Al	500–750 (3)	**TA1201NB1**	300–400	**TA1201NB1M**
Optional Copper and Cu/Al Pressure Type Terminals						
700	Copper	Cu	2/0–500 (2)	**T700NB1**	70–240	**T700NB1M**
1000	Copper	Cu	3/0–500 (3)	**T1000NB1**	95–240	**T1000NB1M**
1200	Copper	Cu	3/0–400 (4)	**T1200NB3**	95–185	**T1200NB3M**

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V**
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor (1200 A) ②	**NGFCT120**
External neutral sensor (800 A) ②	**NGFCT120**
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06**

Base Mounting Hardware

Base mounting hardware is included with a circuit breaker or molded case switch.

Base Mounting Hardware ③

Number of Poles	Description	Catalog Number
Three- and four-pole	Imperial hardware: 0.3125–18 x 1.25 pan-head steel screws and lock washers	**BMH5**
Three- and four-pole	Metric hardware: M8 pan-head steel screws and lock washers	**BMH5M**

Terminal Shield

Terminal Shield

Description	Catalog Number
Three-pole terminal shield	**NTS3K**

Conductor Extension Kit

Conductor Extension Kit ④

Description	Catalog Number
Three-pole both ends Metric	**5104A24G04**
Three-pole both ends English	**5104A24G02**

Keeper Nut

Not required on NG-Frame. Terminals are threaded.

Handle Extension

Included with breaker. Additional handle extensions are available.

Handle Extension

Description	Catalog Number
Single handle extension	**HEX5**

Interphase Barriers

The interphase barriers provide additional electrical clearance between circuit breaker poles for special termination applications. Barriers are high dielectric insulating plates that are installed in the molded slots between the terminals. (Field installation only.)

Interphase Barriers

Description	Catalog Number
Interphase barriers ④	**IPB5**

Notes

① Single terminals individually packed.
② Required for four-wire systems if neutral protection is desired. Sold separately.
③ Metric hardware included with breaker.
④ Included as standard on 100% rated 1200 A breakers only.

Accessories

2

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

NG-Frame Accessories

Description	Reference Page	Three-Pole			Four-Pole			
		Left	Center	Right	Left	Center	Right	Neu.
Internal Accessories (Only One Internal Accessory Per Pole)								
Alarm lockout (Make/Break)	**V4-T2-109**	●		■	●		■	
Auxiliary switch (1A, 1B)	**V4-T2-109**	●		■	●		■	
Auxiliary switch (2A, 2B)	**V4-T2-109**	●		■	●		■	
Auxiliary switch and alarm switch combination	**V4-T2-109**	●		■	●		■	
Shunt trip—standard	**V4-T2-109**	■			■			
Undervoltage release mechanism	**V4-T2-110**	■			■			
External Accessories								
Base mounting hardware	**V4-T2-69**	●	●	●	●	●	●	●
Interphase barriers	**V4-T2-69**	●	●	●	●	●	●	●
Non-padlockable handle block	**V4-T2-107**		■			■		
Padlockable handle lock hasp	**V4-T2-107**	❑		❑	❑		❑	
Key interlock kit	**V4-T2-107**	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-107**	●	●	●				
Electrical operator	**V4-T2-107**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-114**	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-107**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-415**	●	●	●	●	●	●	●
Drawout cassette	**V4-T2-115**	●	●	●	●	●	●	●
Handle extension	**V4-T2-69**	●	●	●	●	●	●	●
Ammeter/cause of trip display	**V4-T2-106**	●	●	●	●	●	●	●
Cause of trip LED module	**V4-T2-106**	●	●	●	●	●	●	●
Digitrip 310+ test kit	**V4-T2-106**	●	●	●	●	●	●	●
Modifications (Refer to Eaton)								
Moisture fungus treatment	**V4-T2-105**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/Naval application, UL 489 Supplement SA and SB	①	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Note

① Contact Eaton.

Technical Data and Specifications

Interrupting Capacity Ratings

UL 489/IEC 60947-2 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240 (UL)	220–240		380–415		480	600	690	
			I_{cu}	I_{cs}	I_{cu}	I_{cs}			I_{cu}	I_{cs}
NGS ①	2, 3, 4	65	85	85	50	50	50	25	20	10
NGH	2, 3, 4	100	100	100	70	50	65	35	25	13
NGC	2, 3, 4	200	200	100	100	50	100	65	35	18
NGU	3, 4	200	—	—	—	—	150	65	—	—

NG-Frame Digitrip Specifications

NG 310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	NG
Frames available	800 A, 1200 A
Continuous current range (A)	320–1200A
Ground fault pickup (A)	160–1200A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100, 150
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash reduction maintenance system (or maintenance mode)	Yes
Interchangeable trip unit	No
High load alarm (suffix B20) ②	Yes
Ground fault alarm with trip (suffix B21) ②	Yes
Ground fault alarm, no trip (suffix B22) ②	Yes
Zone selective interlocking (suffix ZG)	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes
Thru-cover accessories	No

Notes

① 1600 amperes is not a UL or CSA listed rating. 1200 amperes is the maximum UL and CSA rating for NG.

② B2x suffixes cannot be combined with B2x suffixes.

NG 310+ Adjustability Specifications

310+ Settings		NG Frame 800 A	1200 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r		
	A	320	500
	B	400	600
	C	450	630
	D	500	700
	E	600	800
	F	630	900
	G	700	1000
	H (= I_n)	800	1200
t_r = long delay time (seconds) (All 310+)	Position 1	2	2
	Position 2	4	4
	Position 3	6	7
	Position 4	8	10
	Position 5	10	12
	Position 6	12	15
	Position 7	14	20
	Position 8	14	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x	2x
	Position 2	3x	3x
	Position 3	4x	4x
	Position 4	5x	5x
	Position 5	6x	6x
	Position 6	7x	7x
	Position 7	8x	8x
	Position 8	9x	9x
	Position 9	9x	9x
t_{sd} = short delay time I^2t (milliseconds) (LS, LSG)	Fixed	67 at10x	67 at10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG, ALSI, ALSIG) ①	Position 1	Inst	Inst
	Position 2	120	120
	Position 3	300	300
I_g = gound fault pickup (amperes) (LSG, LSIG, ALSIG)	Position 1	160	240
	Position 2	240	360
	Position 3	320	480
	Position 4	480	720
	Position 5	640	960
	Position 6	800	1200
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst	Inst
	Position 2	120	120
	Position 3	300	300
Independently Adjustable Instantaneous (I_i) setting (ALSI, ALSIG)	Yes	2.5x, 4x, 6x, 7x, 8x, 10x, 18x	2.5x, 4x, 6x, 7x, 8x, 10x, 12x
Maintenance Mode (remote) pickup (2.5 x I_n) (ALSI, ALSIG) ②	Fixed	2.5x	2.5x

Notes

① 50 ms for ALSI and ALSIG trip units.

② Maintenance Mode is enabled remotely using a 24 Vdc circuit.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

NG-Frame

Number of Poles	Width	Height	Depth
3	8.25 (209.6)	16.00 (406.4)	5.50 (139.7)
4	11.13 (282.6)	16.00 (406.4)	5.50 (139.7)

NG-Frame

Front Cover Cutout



Front View Three-Pole



Side View



Approximate Shipping Weight in Lbs (kg)

NG-Frame

Breaker Type	Complete Breaker Three-Pole	Four-Pole
NGS, NGH, NGC	45 (20.4)	58 (26.3)

RG-Frame (800–2500 Amperes)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	
Catalog Number Selection	**V4-T2-75**
Product Selection	**V4-T2-76**
Accessories	**V4-T2-81**
Technical Data and Specifications	**V4-T2-82**
Dimensions and Weights	**V4-T2-84**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

RG-Frame (800–2500 Amperes)

Product Description

- Eaton's RG-Frame circuit breakers are available as frame (which includes trip unit), rating plug and terminals
- All R-Frame circuit breakers are suitable for reverse feed use

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

70 kA at 415 Vac and 65 kA at 480 Vac

RG Circuit Breaker With 310+ Electronic Trip Unit



RG 310+ Electronic Trip Unit



RG Circuit Breaker with OPTIM 610 and 910 Electronic Trip Unit



Product Selection

2

70 kA at 415 Vac and 65 kA at 480 Vac

Type RGH with Digitrip 310+ High Interrupting Capacity—U_e Maximum 690 Vac, 70 kA I_{cu} at 415 Vac

See 310+ adjustability specifications on **Page V4-T2-83**.

Maximum Continuous Ampere Rating at 40 °C ①	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 310+ Electronic Trip Unit with Adjustable Rating Plugs—Catalog Number ②						
		LS	LSI	LSG ③	LSIG ③	ALSI	ALSIG	Neutral CT for LSG and LSIG ④
1600 ①	3	**RGH316033E**	**RGH316032E**	**RGH316035E**	**RGH316036E**	**RGH316038E**	**RGH316039E**	**RGFCT160A**
2000	3	**RGH320033E**	**RGH320032E**	**RGH320035E**	**RGH320036E**	**RGH320038E**	**RGH320039E**	**RGFCT200A**
2500	3	**RGH325033E**	**RGH325032E**	**RGH325035E**	**RGH325036E**	**RGH325038E**	**RGH325039E**	**RGFCT250A**

100 kA at Both 415 Vac and 480 Vac

Type RGH with Digitrip 310+ High Interrupting Capacity—U_e Maximum 690 Vac, 70 kA I_{cu} at 415 Vac

See 310+ adjustability specifications on **Page V4-T2-83**.

Maximum Continuous Ampere Rating at 40 °C ①	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 310+ Electronic Trip Unit with Adjustable Rating Plugs—Catalog Number ②					
		LS	LSI	LSG ③⑤	LSIG ③⑤	ALSI	ALSIG ③⑤
1600 ①	4 ⑥	**RGH416033E**	**RGH416032E**	—	—	**RGH416038E**	—
2000	4 ⑥	**RGH420033E**	**RGH420032E**	—	—	**RGH420038E**	—
2500	4 ⑥	**RGH425033E**	**RGH425032E**	—	—	**RGH425038E**	—

Notes

① For SCR application, use 2000 ampere frame.

② Order terminals separately. Mounting hardware not included.

③ Ground fault equipped trip units available with remote indicating panel. Add "R" to catalog number, for example, "**RGH316035RW**."

④ Required for four-wire systems if neutral protection is desired. Sold separately.

⑤ No neutral protection available on four-pole breakers with LSG or LSIG trip units.

⑥ Unprotected left pole neutral. Add "P" to catalog number for 100% protected left pole neutral, add "E" for 60% protected, for example, "**RGH416033PW**," "**RGH416033EW**."

RG MCCBs have English threading on line and load conductors. Use suffix "M" for metric threading.

100 kA at Both 415 Vac and 480 Vac

Type RGC with Digitrip 310+ Very High Interrupting Capacity—U_e Maximum 690 Vac, 100 kA I_{cu} at 415 Vac

See 310+ adjustability specifications on **Page V4-T2-83**.

Maximum Continuous Ampere Rating at 40 °C ①	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 310+ Electronic Trip Unit with Adjustable Rating Plugs—Catalog Number ②						
		LS	LSI	LSG ③	LSIG ③	ALSI	ALSIG	Neutral CT for LSG and LSIG ④
1600 ①	3	**RGC316033E**	**RGC316032E**	**RGC316035E**	**RGC316036E**	**RGC316038E**	**RGC316039E**	**RGFCT160A**
2000	3	**RGC320033E**	**RGC320032E**	**RGC320035E**	**RGC320036E**	**RGC320038E**	**RGC320039E**	**RGFCT200A**
2500	3	**RGC325033E**	**RGC325032E**	**RGC325035E**	**RGC325036E**	**RGC325038E**	**RGC325039E**	**RGFCT250A**

Type RGC with Digitrip 310+ Very High Interrupting Capacity—U_e Maximum 690 Vac, 100 kA I_{cu} at 415 Vac, continued

See 310+ adjustability specifications on **Page V4-T2-83**.

Maximum Continuous Ampere Rating at 40 °C ①	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 310+ Electronic Trip Unit with Adjustable Rating Plugs—Catalog Number ②					
		LS	LSI	LSG ③⑤	LSIG ③⑤	ALSI	ALSIG ③⑤
1600 ①	4 ⑥	**RGC416033E**	**RGC416032E**	—	—	**RGC416038E**	—
2000	4 ⑥	**RGC420033E**	**RGC420032E**	—	—	**RGC420038E**	—
2500	4 ⑥	**RGC425033E**	**RGC425032E**	—	—	**RGC425038E**	—

Molded Case Switches ⑦

Ampere Rating	Number of Poles	Catalog Number
1600	3	**RGK3160KSE**
2000	3	**RGK3200KSE**
1600	4	**RGK4160KSE**
2000	4	**RGK4200KSE**

Notes

① For SCR application, use 2000 ampere frame.
② Order terminals separately. Mounting hardware not included.
③ Ground fault equipped trip units available with remote indicating panel. Add "R" to catalog number, for example, "**RGH316035RW**."
④ Required for four-wire systems if neutral protection is desired. Sold separately.
⑤ No neutral protection available on four-pole breakers with LSG or LSIG trip units.
⑥ Unprotected left pole neutral. Add "P" to catalog number for 100% protected left pole neutral, add "E" for 60% protected, for example, "**RGH416033PW**," "**RGH416033EW**."
⑦ Molded case switch will trip above 17,500 amperes.

RG MCCBs have English threading on line and load conductors. Use suffix "M" for metric threading.

Type RG with Digitrip 610 and 910

Maximum Continuous Ampere Rating at 40 °C	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 610 and 910 Electronic Trip Unit with Rating Plugs Order as Individual Component—Catalog Number ① L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S –Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G –Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)						Digitrip RMS Interchangeable Rating Plug (Order as Individual Component)	
		LI	LS	LSI	LIG	LSG	LSIG	Fixed Rating Plug	
Long Delay Pickup		0.5–1.0 x I_n	0.5–I.0$_n$	0.5–1.0 x I_n	0.5–1.0 x I_n	0.5–1.0 x I_n	0.5–1.0 x I_n		
Long Delay Time		2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds		
Short Time Range		2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r		
Short Time Delay		—	100–500 ms	100–500 ms	—	100–500 ms	100–500 ms		
Instantaneous		2–6 x M1 and M2	—	2–6 x M1 and M2	2–6 x M1 and M2	—	2–6 x M1 and M2		
Ground Fault Pickup		—	—	—	0.25–1.0 x I_n ②	0.25–1.0 x I_n ②	0.25–1.0 x I_n ②	Ampere Rating	Catalog Number
Ground Fault Delay		—	—	—	100–500 ms	100–500 ms	100–500 ms		
Type RGH with Digitrip 610 High Interrupting Capacity—U_e Max. 690 Vac, 70 kA I_{cu} at 415 Vac									
1600	3	**RGH316T61WP44**	**RGH316T63WP44**	**RGH316T62WP44**	**RGH316T64WP44**	**RGH316T65WP44**	**RGH316T66WP44**	800	**RP6R16A080**
								1000	**RP6R16A100**
								1200	**RP6R16A120**
								1250	**RP6R16A125**
		Includes 1600 A rating plug						1600	**RP6R16A160**
2000	3	**RGH320T61WP49**	**RGH320T63WP49**	**RGH320T62WP49**	**RGH320T64WP49**	**RGH320T65WP49**	**RGH320T66WP49**	1000	**RP6R20A100**
								1200	**RP6R20A120**
								1250	**RP6R20A125**
								1600	**RP6R20A160**
		Includes 2000 A rating plug						2000	**RP6R20A200**
2500	3	**RGH325T61WP53**	**RGH325T63WP53**	**RGH325T62WP53**	**RGH325T64WP53**	**RGH325T65WP53**	**RGH325T66WP53**	1600	**RP6R25A160**
								2000	**RP6R25A200**
								2500	**RP6R25A250**
Type RGC with Digitrip 610 Very High Interrupting Capacity—U_e Max. 690 Vac, 100 kA I_{cu} at 415 Vac									
1600	3	**RGC316T61WP44**	**RGC316T63WP44**	**RGC316T62WP44**	**RGC316T64WP44**	**RGC316T65WP44**	**RGC316T66WP44**	800	**RP6R16A080**
								1000	**RP6R16A100**
								1200	**RP6R16A120**
								1250	**RP6R16A125**
		Includes 1600 A rating plug						1600	**RP6R16A160**
2000	3	**RGC320T61WP49**	**RGC320T63WP49**	**RGC320T62WP49**	**RGC320T64WP49**	**RGC320T65WP49**	**RGC320T66WP49**	1000	**RP6R20A100**
								1200	**RP6R20A120**
								1250	**RP6R20A125**
								1600	**RP6R20A160**
		Includes 2000 A rating plug						2000	**RP6R20A200**
2500	3	**RGC325T61WP53**	**RGC325T63WP53**	**RGC325T62WP53**	**RGC325T64WP53**	**RGC325T65WP53**	**RGC325T66WP53**	1600	**RP6R25A160**
								2000	**RP6R25A200**
		Includes 2500 A rating plug						2500	**RP6R25A250**

Notes

① Order terminals separately. Mounting hardware not included.

② Not to exceed 1200 ampere ground fault pickup.

RG MCCBs have metric threading on line and load conductors. Use RD MCCBs if imperial threading is required.

Type RG with Digitrip 610 and 910, continued

Maximum Continuous Ampere Rating at 40 °C	Number of Poles	Circuit Breaker Frame Including Digitrip RMS 610 and 910 Electronic Trip Unit with Rating Plugs Order as Individual Component—Catalog Number ①						Digitrip RMS Interchangeable Rating Plug (Order as Individual Component)	
		L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S –Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G –Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)							
		LI	LS	LSI	LIG	LSG	LSIG	Fixed Rating Plug	
Long Delay Pickup		0.5–1.0 x I_n	0.5–I.0$_n$	0.5–1.0 x I_n	0.5–1.0 x I_n	0.5–1.0 x I_n	0.5–1.0 x I_n		
Long Delay Time		2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds	2–24 Seconds		
Short Time Range		2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r	2–6 x I_r		
Short Time Delay		—	100–500 ms	100–500 ms	—	100–500 ms	100–500 ms		
Instantaneous		2–6 x M1 and M2	—	2–6 x M1 and M2	2–6 x M1 and M2	—	2–6 x M1 and M2		
Ground Fault Pickup		—	—	—	0.25–1.0 x In ②	0.25–1.0 x In ②	0.25–1.0 x In ②		
Ground Fault Delay		—	—	—	100–500 ms	100–500 ms	100–500 ms		
								Ampere Rating	Catalog Number
Type RGH with Digitrip 910 High Interrupting Capacity—U_e Max. 690 Vac, 70 kA I_{cu} at 415 Vac									
1600	3	**RGH316T91WP44**	**RGH316T93WP44**	**RGH316T92WP44**	**RGH316T94WP44**	**RGH316T95WP44**	**RGH316T96WP44**	800	**RP6R16A080**
								1000	**RP6R16A100**
								1200	**RP6R16A120**
								1250	**RP6R16A125**
		Includes 1600 A rating plug						1600	**RP6R16A160**
2000	3	**RGH320T91WP49**	**RGH320T93WP49**	**RGH320T92WP49**	**RGH320T94WP49**	**RGH320T95WP49**	**RGH320T96WP49**	1000	**RP6R20A100**
								1200	**RP6R20A120**
								1250	**RP6R20A125**
								1600	**RP6R20A160**
		Includes 2000 A rating plug						2000	**RP6R20A200**
2500	3	**RGH325T91WP53**	**RGH325T93WP53**	**RGH325T92WP53**	**RGH325T94WP53**	**RGH325T95WP53**	**RGH325T96WP53**	1600	**RP6R25A160**
								2000	**RP6R25A200**
		Includes 2500 A rating plug						2500	**RP6R25A250**
Type RGC with Digitrip 910 Very High Interrupting Capacity—U_e Max. 690 Vac, 100 kA I_{cu} at 415 Vac									
1600	3	**RGC316T91WP44**	**RGC316T93WP44**	**RGC316T92WP44**	**RGC316T94WP44**	**RGC316T95WP44**	**RGC316T96WP44**	800	**RP6R16A080**
								1000	**RP6R16A100**
								1200	**RP6R16A120**
								1250	**RP6R16A125**
		Includes 1600 A rating plug						1600	**RP6R16A160**
2000	3	**RGC320T91WP49**	**RGC320T93WP49**	**RGC320T92WP49**	**RGC320T94WP49**	**RGC320T95WP49**	**RGC320T96WP49**	1000	**RP6R20A100**
								1200	**RP6R20A120**
								1250	**RP6R20A125**
								1600	**RP6R20A160**
		Includes 2000 A rating plug						2000	**RP6R20A200**
2500	3	**RGC325T91WP53**	**RGC325T93WP53**	**RGC325T92WP53**	**RGC325T94WP53**	**RGC325T95WP53**	**RGC25T96WP53**	1600	**RP6R25A160**
								2000	**RP6R25A200**
		Includes 2500 A rating plug						2500	**RP6R25A250**

Notes

① Order terminals separately. Mounting hardware not included.

② Not to exceed 1200 ampere ground fault pickup.

RG MCCBs have metric threading on line and load conductors. Use RD MCCBs if imperial threading is required.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

R-Frame circuit breakers use Cu/Al terminals as standard and copper only terminals as an option. Specify if factory installation is required. Must have terminals for 100% rated and or freeze testing requirements.

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	Hardware	AWG/kcmil Wire Range/ Number of Conductors	Metric Wire Range mm²	Catalog Number
Wire Terminals						
1600	Aluminum	Cu/Al	Metric	500–1000 (4)	300–500	**TA1600RDM** ①
1600	Copper	Cu	Metric	1–600 (4)	50–300	**T1600RDM** ①
2000	Aluminum	Cu/Al	Metric	2–600 (6)	35–300	**TA2000RDM** ②
Rear Connectors						
2000	Copper	—	Metric	—	—	**B2016RDM** ①
2000	Copper	—	Metric	—	—	**B2016RDLM** ①
2500	Copper	—	Metric	—	—	**B2500RDM** ①

RG Rear Connector Exploded View



TA2000RD Wire Terminal

Note: Order one TA2000RDM kit per three poles. Catalog number includes bus connection, terminals and hardware for either line side or load side of three-pole breaker.



Base Mounting Hardware

Supplied by customer.

Handle Extension

Included with breaker. Additional handle extensions are available.

Handle Extension

Description	Catalog Number
Single handle extension	**HEX6**

Wire Seal

The wire seal can be used to secure the cover on the trip unit to prevent adjustments after settings are confirmed.

Wire Seal

Description	Catalog Number
Wire seal	**5108A03H01**

Notes

① Order one per pole—single terminals individually packed.

② Order one TA2000RD kit per three poles. Catalog number includes bus connection, terminals and hardware for either line side or load side of three-pole breaker.

③ For use with 2500 A Frame. Do not order separately unless for replacement purposes. Included in breaker carton when 2500 A frame is ordered.

RG MCCBs have metric threading on line and load conductors. Use RD MCCBs if imperial threading is required.

Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

RG-Frame Accessories

Description	Reference Page	Three-Pole			Four-Pole			
		Left	Center	Right	Left	Center	Right	Neutral
Internal Accessories (Only One Internal Accessory Per Pole)								
Alarm lockout (Make/Break)	**V4-T2-109**			■			■	
Auxiliary switch (1A, 1B)	**V4-T2-109**			■			■	
Auxiliary switch (2A, 2B)	**V4-T2-109**			■			■	
Auxiliary switch and alarm switch combination	**V4-T2-109**			■			■	
Shunt trip—standard	**V4-T2-109**			●			●	
Undervoltage release mechanism	**V4-T2-110**			●			●	
External Accessories								
Base mounting hardware	**V4-T2-80**	●	●	●	●	●	●	●
Padlockable handle lock hasp	**V4-T2-107**	❑		❑	❑		❑	
Key interlock kit	**V4-T2-107**	❑		❑	❑		❑	
Electrical operator	**V4-T2-107**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-415**	●	●	●	●	●	●	●
Handle extension	**V4-T2-80**	●	●	●	●	●	●	●
Digitrip 310+ test kit	**V4-T2-106**	●	●	●	●	●	●	●
Modifications (Refer to Eaton)								
Moisture fungus treatment	**V4-T2-105**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application, UL 489 Supplement SA and SB	①	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V**
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor (2500 A) ②	**RGFCT250A**
External neutral sensor (2000 A) ②	**RGFCT200A**
External neutral sensor (1600 A) ②	**RGFCT160A**
Breaker-mount cause-of-trip indication ③	—
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06**

Notes

① Contact Eaton.
② Required for four-wire systems if neutral protection is desired. Sold separately.
③ Cause-of-trip indication LEDs integrated in RG 310+ trip units.

Technical Data and Specifications

UL 489/CSA Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600
RGH	3, 4	125	—	65	50
RGC	3, 4	200	—	100	65

IEC 947-2 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	415	690
RGH	3, 4			
I_{cu}		135	70	25
I_{cs}		100	50	13
RGC	3, 4			
I_{cu}		200	100	35
I_{cs}		100	50	18

RG 310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	RG
Frames available	1600 A, 2000 A, 2500 A
Continuous current range (A)	800–2500 A
Ground fault pickup (A)	200–1200 A
Interrupting capacities at 480 Vac (kAIC)	65, 100
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash reduction maintenance system (or maintenance mode)	Yes
Interchangeable trip unit	Yes
High load alarm (suffix B20) ②	Yes
Ground fault alarm with trip (suffix B21) ②	Yes
Ground fault alarm, no trip (suffix B22) ②	Yes
Zone selective interlocking (suffix ZG)	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes
Thru-cover accessories	No

Notes

① Utilization Category A circuit breakers.

② B2x suffixes cannot be combined with B2x suffixes.

See **Page V4-T2-74** for trip unit specifications.

RG 310+ Adjustability Specifications

310+ Settings		RG Frame 1600 A	2000 A	2500 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r			
	A	800	1000	1600
	B	900	1200	1700
	C	1000	1400	1800
	D	1100	1600	2000
	E	1200	1700	2100
	F	1400	1800	2200
	G	1500	1900	2400
	H (= I_n)	1600	2000	2500
t_r = long delay time (seconds) (All 310+)	Position 1	2	2	2
	Position 2	4	4	4
	Position 3	7	7	7
	Position 4	10	10	10
	Position 5	12	12	12
	Position 6	15	15	15
	Position 7	20	20	20
	Position 8	24	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x	2x	2x
	Position 2	3x	3x	2x
	Position 3	4x	4x	2x
	Position 4	5x	5x	3x
	Position 5	6x	6x	4x
	Position 6	7x	7x	5x
	Position 7	8x	8x	6x
	Position 8	8x	8x	6x
	Position 9	9x	9x	6x
t_{sd} = short delay time I^2t (milliseconds) (LS, LSG)	Fixed	67 at10x	67 at10x	67 at10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG, ALSI, ALSIG) ①	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
I_g = ground fault pickup (amperes) (LSG, LSIG, ALSIG)	Position 1	200	200	200
	Position 2	400	400	400
	Position 3	600	600	600
	Position 4	800	800	800
	Position 5	1000	1000	1000
	Position 6	1200	1200	1200
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
Independently Adjustable Instantaneous (I_i) setting (ALSI, ALSIG)	Yes	2.5x, 4x, 6x, 7x, 8x, 11x	2.5x, 4x, 6x, 7x, 8x, 9x	2.5x, 4x, 6x, 7x
Maintenance Mode (remote) pickup (2.5 x I_n) (ALSI, ALSIG) ②	Fixed	2.5x	2.5x	2.5x

Notes

① 50 ms for ALSI and ALSIG trip units.

② Maintenance Mode is enabled remotely using a 24 Vdc circuit.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

RG-Frame

Number of Poles	Width	Height	Depth
3	15.50 (393.7)	16.00 (406.4)	9.75 (247.7)
4	20.00 (508.0)	16.00 (406.4)	9.75 (247.7)



Approximate Shipping Weight in Lbs (kg)

RG-Frame

Breaker Type	Complete Breaker Number of Poles Three-Pole	Four-Pole
1600 Amperes		
RGH, RGC	102 (46.3)	135 (61.2)
2000 Amperes		
RGH, RGC	102 (46.3)	135 (61.2)
2500 Amperes		
RGH, RGC	135 (61.2)	182 (82.6)

Motor Circuit 480 Vac, Protectors

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP) Product Selection Guide and Ordering Information	**V4-T2-86**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Motor Circuit Protectors (MCP)

Product Selection Guide and Ordering Information

EG-Frame—480 Vac, 600Y/347 Vac Maximum ①

Continuous Amperes	Cam Setting	Motor Full Load Current Amperes ②	MCP Trip Setting ③	MCP Catalog Number
3	A	0.69 –0.91	9	**HMCPE003A0C**
	B	1.1–1.3	15	
	C	1.6–1.7	21	
	D	2.0–2.2	27	
	E	2.3–2.5	30	
	F	2.6– 2.8	33	
7	A	1.5–2.0	21	**HMCPE007C0C**
	B	2.6–3.1	35	
	C	3.7–3.9	49	
	D	4.8–5.2	63	
	E	5.3–5.7	70	
	F	5.8–6.1	77	
15	A	3.4–4.5	45	**HMCPE015E0C**
	B	5.7–6.8	75	
	C	8.0–9.1	105	
	D	10.4–11.4	135	
	E	11.5–12.6	150	
	F	12.7–13.0	165	
30	A	3.9–9.1	90	**HMCPE030H1C**
	B	11.5–13.7	150	
	C	16.1–18.3	210	
	D	20.7–22.9	270	
	E	23.0–25.2	300	
	F	25.3–26.1	330	

Notes

① UL listed for use with Eaton Motor Starters.

② Motor FLA ranges are typical. The corresponding trip setting is at 13 times the minimum FLA value shown.
Where a 13 times setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

③ For DC applications, actual trip levels are approximately 40% higher than values shown.

EG-Frame—480 Vac, 600Y/347 Vac Maximum, continued ①

Continuous Amperes	Cam Setting	Motor Full Load Current Amperes ②	MCP Trip Setting ③	MCP Catalog Number
50	A	11.5–15.2	150	**HMCPE050K2C**
	B	19.2–22.9	250	
	C	26.9–30.6	350	
	D	34.6–38.3	450	
	E	38.4–42.1	500	
	F	42.2–43.5	550	
70	A	16.1–30.6	210	**HMCPE070M2C**
	B	26.9–32.2	350	
	C	37.6–42.9	490	
	D	48.4–53.7	630	
	E	53.8–59.1	700	
	F	59.2–60.9	770	
100	A	23.0–30.6	300	**HMCPE100R3C**
	B	38.4–46.0	500	
	C	53.8–61.4	700	
	D	69.2–76.8	900	
	E	76.9–84.5	1000	
	F	84.6–87.0	1100	
100	A	38.4–46.0	500	**HMCPE100T3C**
	B	57.6–65.2	750	
	C	76.9–84.5	1000	
	D	④	1250	
	E	④	1375	
	F	④	1500	

JG-Frame—600 Vac Maximum, 250 Vdc Maximum ①

Continuous Amperes	MCP Trip Range (Amperes)	MCP Catalog Number
250	500–1000	**HMCPJ250D5L**
	625–1250	**HMCPJ250F5L**
	750–1500	**HMCPJ250G5L**
	875–1750	**HMCPJ250J5L**
	1000–2000	**HMCPJ250K5L**
	1125–2250	**HMCPJ250L5L**
	1250–2500	**HMCPJ250W5L**

Notes

① UL listed for use with Eaton Motor Starters.

② Motor FLA ranges are typical. The corresponding trip setting is at 13 times the minimum FLA value shown. Where a 13 times setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

③ For DC applications, actual trip levels are approximately 40% higher than values shown.

④ Settings above 10 x I_n are for special applications. Where the ampere rating of the disconnecting means cannot be less than 115% of the motor full load ampere rating.

LG-Frame—600 Vac Maximum, 250 Vdc Maximum ①

Continuous Amperes	MCP Trip Range (Amperes)	MCP Catalog Number
600	1250–2500	**HMCPL600L6G**
	1500–3000	**HMCPL600N6G**
	1750–3500	**HMCPL600R6G**
	2000–4000	**HMCPL600X6G**
	2250–4500	**HMCPL600Y6G**
	2500–5000	**HMCPL600P6G**
	3000–6000	**HMCPL600M6G**

Notes

① UL listed for use with Eaton Motor Starters.

800 and 1200 ampere, 600 Vac maximum motor circuit protectors are available as Series C HMCP product.

Series G Motor Protector Circuit Breakers (MPCB)

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	
Product Selection	**V4-T2-90**
Technical Data and Specifications	**V4-T2-91**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Motor Protector Circuit Breakers (MPCB)

Product Description

- Eliminates need for separate overload relay

Application Description

- Can be used with contactor to eliminate need for overload relay and still create manual motor control
- Meets requirement for motor branch protection, including:
  - Disconnecting means
  - Branch circuit short circuit protection
  - Overload protection

Features and Benefits

- Phase unbalance protection
- Phase loss protection
- Hot trip/cold trip
- High load alarm
- Pre-detection trip relay option
- Class 10, 15, 20, 30 protection

Standards and Certifications

- IEC 60947-2
- UL 489 100% rated
- UL 508
- CSA C22.2

Listed

Product Selection

JGMP Catalog Numbers

Continuous Amperes	35 kAIC Catalog Number	65 kAIC Catalog Number
50	**JGMPS050G**	**JGMPH050G**
100	**JGMPS100G**	**JGMPH100G**
160	**JGMPS160G**	**JGMPH160G**
250	**JGMPS250G**	**JGMPH250G**

JGMP FLA Ie Dial Setting

Continuous Amperes	A	B	C	D	E	F	G	H
50	20	20	25	30	32	40	45	50
100	40	45	50	63	70	80	90	100
160	63	80	90	100	110	125	150	160
250	100	125	150	160	175	200	225	250

LGMP Catalog Numbers

Continuous Amperes	50 kAIC Catalog Number	65 kAIC Catalog Number
250	**LGMPS250G**	**LGMPH250G**
400	**LGMPS400G**	**LGMPH400G**
600	**LGMPS600G**	**LGMPH600G**
630 ①	**LGMPS630G**	**LGMPH630G**

LGMP FLA Ie Dial Setting

Continuous Amperes	A	B	C	D	E	F	G	H
250	100	125	150	160	175	200	225	250
400	160	200	225	250	300	315	350	400
600	250	300	315	350	400	450	500	600
630 ①	250	300	315	350	400	500	600	630

Notes

① 630 amperes is not a UL listed rating. 600 amperes is the maximum UL or CSA for LG breaker.

For pre-trip alarm option, order Style Number 5721B31G02.

For additional breaker solutions, see **Page V4-T2-267**.

Technical Data and Specifications

JGMPS and JGMPH Rating and Ampere Range

Breaker Capacity (kA rms) AC 50–60 Hz			Maximum Rated Current—250 A Breaker Type JGMPS	JGMPH
IEC 60947-2	220–240 Vac	I cu	85	100
		I cs	85	100
	380–415 Vac	I cu	40	70
		I cs	40	70
	660–690 Vac	I cu	12	14
		I cs	6	7
NEMA UL 489	240 Vac		85	100
	480 Vac		35	65
	600 Vac		25	35
Number of poles			3	3
Ampere range			50–250	50 –250

LGMPS and LGMPH Rating and Ampere Range

Breaker Capacity (kA rms) AC 50–60 Hz			Maximum Rated Current—630 A ① Breaker Type LGMPS	LGMPH
IEC 60947-2	220–240 Vac	I cu	85	100
		I cs	85	100
	380–415 Vac	I cu	50	70
		I cs	50	53
	660–690 Vac	I cu	20	25
		I cs	10	13
NEMA UL 489	240 Vac		85	100
	480 Vac		50	65
	600 Vac		25	35
Number of poles			3	3
Ampere range			250–630 ①	250 –630 ①

Notes

① 630 amperes is not a UL listed rating. 600 amperes is the maximum UL or CSA for LG breaker.

For pre-trip alarm option, order Style Number 5721B31G02.

Clockwise from Left:
JG, LG, EG MCCBs Shown with
Ground Fault (Earth Leakage) Module

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	
Product Selection	**V4-T2-93**
Dimensions	**V4-T2-94**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

30 mA Ground Fault (Earth Leakage) Module

Product Description

Eaton offers three- and four-pole 30 mA ground fault (earth leakage) protection modules for Series G E-, J- and L-frame molded case circuit breakers (MCCBs). Separate UL listed and IEC rated devices are available for each frame.

The modules are bottom mounted and are available for each frame circuits up to:

- EG: 125 amperes
- JG: 150 (UL), 160 (IEC) or 250 amperes
- LG: 400, 600 (UL) or 630 (IEC) amperes

The module is completely self contained, including a current sensor, relay and power supply inside the device. Current pickup settings are selectable from 0.03 to 10 amperes for all devices, except for the UL listed module, for which settings are selectable from 0.03 to 30 amperes. Time delays are also selectable from Instantaneous to 1.0 second for pickup settings of 0.10 amperes and above. The current pickup setting of 0.03 amperes defaults to an Instantaneous time setting regardless of the time dial's position.

Two alarm contacts are included with each device, which can be wired externally for remote indication. Both of these are also indicated by an LED on the front of the device:

1. 50% pre-trip: alarms when the earth leakage current reaches 50% of the set pickup setting value.
2. 100% after trip: alarms when the breaker reaches the set pickup setting value and the breaker trips.

UL-Rated LG-Frame Earth Leakage Module Faceplate



IEC-Rated LG-Frame Earth Leakage Module Faceplate



Product Selection

EG-Frame

EG-Frame Ground Fault Modules, UL-Rated (Bottom Mounted, 120–480 Vac, 50/60 Hz) ①

Ampere Rating	Number of Poles	Catalog Number
125	3	**ELEBN3125G**
125	4	**ELEBN4125G**

EG-Frame Earth Leakage Modules, IEC-Rated (Bottom Mounted, 230–415 Vac, 50/60 Hz)

Ampere Rating	Number of Poles	Catalog Number
125	3	**ELEBE3125G**
125	4	**ELEBE4125G**

JG-Frame

JG-Frame Ground Fault Modules, UL-Rated (Bottom Mounted, 120–480 Vac, 50/60 Hz)

Ampere Rating	Number of Poles	Catalog Number
150	3	**ELJBN3150W**
150	4	**ELJBN4150W**
250	3	**ELJBN3250W**
250	4	**ELJBN4250W**

JG-Frame Earth Leakage Modules, IEC-Rated (Bottom Mounted, 230–415 Vac, 50/60 Hz)

Ampere Rating	Number of Poles	Catalog Number
160	3	**ELJBE3160W**
160	4	**ELJBE4160W**
250	3	**ELJBE3250W**
250	4	**ELJBE4250W**

Note

① Shunt trip and undervoltage release cannot be used in an EG breaker connected to an earth leakage module.

LG-Frame

LG-Frame Ground Fault Modules, UL-Rated (Bottom Mounted, 120–480 Vac, 50/60 Hz)

Ampere Rating	Number of Poles	Catalog Number
400	3	**ELLBN3400W**
400	4	**ELLBN4400W**
600	3	**ELLBN3600W**
600	4	**ELLBN4600W**

LG-Frame Earth Leakage Modules, IEC-Rated (Bottom Mounted, 230–415 Vac, 50/60 Hz)

Ampere Rating	Number of Poles	Catalog Number
400	3	**ELLBE3400W**
400	4	**ELLBE4400W**
630	3	**ELLBE3630W**
630	4	**ELLBE4630W**

Dimensions

Approximate Dimensions in Inches (mm)

2

Assembled Breaker and Earth Leakage Module

Frame	Height	Width	Depth
Three-Pole			
EG	10.25 (260.3)	3.00 (76.2)	2.98 (75.8)
JG	11.25 (285.8)	4.13 (104.9)	3.57 (90.7)
LG	15.38 (390.7)	5.48 (139.2)	4.06 (103.1)
Four-Pole			
EG	10.25 (260.3)	4.00 (101.6)	2.98 (75.8)
JG	11.25 (285.8)	5.50 (139.7)	3.57 (90.7)
LG	15.38 (390.7)	7.23 (183.6)	4.06 (103.1)

EG-Frame With Earth Leakage Module



JG-Frame With Earth Leakage Module



LG-Frame With Earth Leakage Module



Current Limiting Circuit Breaker Modules

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	
Product Selection	**V4-T2-97**
Technical Data and Specifications	**V4-T2-98**
Dimensions and Weights	**V4-T2-98**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Current Limiting Circuit Breaker Module

Product Overview

Power demand continues to grow in new and existing facilities. To meet increased demand, larger utility supplies, spot networks and large facility transformers are installed. The increased capacity of the electrical source results in increased fault currents in excess of 100 kA short-circuit protection. Eaton manufactures non-fused current limiting modules with interrupting capacities up to 200 kA at 600 Vac or 70 kA at 690 Vac. Unlike fused current limiters with a one-time use, a current limiter module provides an automatic reset of the module after a short-circuit event. Resetting the molded-case circuit breaker is the only action required to restore critical power to the system; there is no time wasted with sourcing the correct replacement fuses or module to bring system back online.

Product Description

The current limiting breaker modules use a unique contact design to enhance the system protection similar to that of the circuit breaker. When high short-circuit current is flowing through the contacts of these modules, the design results in very high interrupting capacities and improved current limiting characteristics.

Application Description

High-performance breakers are most commonly applied when very high fault levels are available and with applications where the current limiting capability is used upstream of the final load to limit current. Typical loads include lighting, power distribution, and motor control applications.

Features and Benefits

Superior system protection:

- Auto reset improves system uptime and eliminates the need for finding replacement parts
- No fuses to replace, reducing the overall cost of ownership and the waste created by fuses
- Overloads, by using inverse time current tripping characteristics of the molded-case circuit breaker
- Low-level short circuits, by using instantaneous and/or short-time delay tripping characteristics of the molded-case circuit breaker
- High-level short circuits, by using ultra-high-speed, blow-apart contacts of the current limiting module in series with the circuit breaker contacts
- Let-through currents, by improved opening speed of the contacts, the resultant rapid rise of arc voltage introduces impedance into the system

Standards and Certifications

- IEC 60947-2
- UL 489
- CSA C22.2

Listed

Product Selection

Series G High Performance Family Offering

Type	Product	Amperes	480 Vac (UL)	600 Vac (UL)	415 Vac (IEC) I_{cu}	415 Vac (IEC) I_{cs}	690 Vac (IEC) I_{cu}	690 Vac (IEC) I_{cs}
EGC 3P thermal-magnetic	Breaker only	15–125	100	35 ①	100	100	—	—
	With limiter	15–100	150	100 ①	150	150	—	—
JG 3P thermal-magnetic	Breaker only	70–250	200	50	200	200	18	14
	With limiter	70–225	200	200	200	150	70	18
JG 3P electronic	Breaker only	20–250	200	50	200	200	18	14
	With limiter	100–250	200	200	200	150	70	18
LG 3P thermal-magnetic	Breaker only	250–600	200	65	200	200	35	18
LG3P electronic	Breaker only	100–600	200	65	200	200	35	18

EG-Frame

EG IC Rating—150 kAIC at 415 and 480 Vac

UL Listed (NEMA/IEC Rated) Base Molded Case Circuit Breaker	Breaker with Line Side Mounted Current Limiter	Breaker with Load Side Mounted Current Limiter	Line and Load Terminations Included ②	Interphase Barrier Included for Limiter
EGC3015FFG	**EGC3015FFGQ01**	**EGC3015FFGQ02**	**T125EF**	**EIPBSK**
EGC3016FFG	**EGC3016FFGQ01**	**EGC3016FFGQ02**	**T125EF**	**EIPBSK**
EGC3020FFG	**EGC3020FFGQ01**	**EGC3020FFGQ02**	**T125EF**	**EIPBSK**
EGC3025FFG	**EGC3025FFGQ01**	**EGC3025FFGQ02**	**T125EF**	**EIPBSK**
EGC3030FFG	**EGC3030FFGQ01**	**EGC3030FFGQ02**	**T125EF**	**EIPBSK**
EGC3032FFG	**EGC3032FFGQ01**	**EGC3032FFGQ02**	**T125EF**	**EIPBSK**
EGC3035FFG	**EGC3035FFGQ01**	**EGC3035FFGQ02**	**T125EF**	**EIPBSK**
EGC3040FFG	**EGC3040FFGQ01**	**EGC3040FFGQ02**	**T125EF**	**EIPBSK**
EGC3045FFG	**EGC3045FFGQ01**	**EGC3045FFGQ02**	**T125EF**	**EIPBSK**
EGC3050FFG	**EGC3050FFGQ01**	**EGC3050FFGQ02**	**T125EF**	**EIPBSK**
EGC3060FFG	**EGC3060FFGQ01**	**EGC3060FFGQ02**	**T125EF**	**EIPBSK**
EGC3063FFG	**EGC3063FFGQ01**	**EGC3063FFGQ02**	**T125EF**	**EIPBSK**
EGC3070FFG	**EGC3070FFGQ01**	**EGC3070FFGQ02**	**T125EF**	**EIPBSK**
EGC3080FFG	**EGC3080FFGQ01**	**EGC3080FFGQ02**	**T125EF**	**EIPBSK**
EGC3090FFG	**EGC3090FFGQ01**	**EGC3090FFGQ02**	**T125EF**	**EIPBSK**
EGC3100FFG	**EGC3100FFGQ01**	**EGC3100FFGQ02**	**T125EF**	**EIPBSK**

Notes

① 600Y/347V.

② Two interphase barriers included on line end mounted limiter; (2) line end of limiter. Four interphase barriers included on load end mounted limiter; (2) line end of breaker (2) load end of limiter.

Technical Data and Specifications

2

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
EGC…Q	240 V/150 kA	21.80	0.277
EGC…Q	480 V/150 kA	21.80	0.277
EGC…Q	600 V/100 kA	22.60	0.387

Dimensions and Weights

Approximate Dimensions in Inches (mm)

Assembled Breaker and Current Limiting Module

Frame	Height	Width	Depth	Weight in lbs (kg)
EG	9.66 (245.7)	3.00 (76.2)	2.98 (75.8)	2.91 (1.32)
HMCP	9.66 (245.7)	3.00 (76.2)	2.98 (75.8)	4.18 (1.90)

EG-Frame With Current Limiter Module



JG Frame

JG IC Rating—200 kAIC at 600 Vac and 70 kAIC at 690 Vac

Ampere Rating	Magnetic Range	UL Listed, IEC Rated Breaker With Line Side Mounted Current Limiter ①	UL Listed, IEC Rated Breaker With Load Side Mounted Current Limiter ②	IEC Rated Breaker With Line Side Mounted Current Limiter ①	IEC Rated Breaker With Load Side Mounted Current Limiter ②
		Fixed Thermal, Adjustable Magnetic		**Adjustable Thermal, Adjustable Magnetic**	
70	350–700	**JGH3070FAGQ01**	**JGH3070FAGQ02**	—	—
90	450–900	**JGH3090FAGQ01**	**JGH3090FAGQ02**	—	—
100	500–1000	**JGH3100FAGQ01**	**JGH3100FAGQ02**	**JGH3100AAGQ01**	**JGH3100AAGQ02**
125	625–1250	**JGH3125FAGQ01**	**JGH3125FAGQ02**	**JGH3125AAGQ01**	**JGH3125AAGQ02**
150	750–1550	**JGH3150FAGQ01**	**JGH3150FAGQ02**	—	—
160	800–1600	—	—	**JGH3160AAGQ01**	**JGH3160AAGQ02**
175	875–1750	**JGH3175FAGQ01**	**JGH3175FAGQ02**	—	—
200	1000–2000	**JGH3200FAGQ01**	**JGH3200FAGQ02**	**JGH3200AAGQ01**	**JGH3200AAGQ02**
225	1125–2250	**JGH3225FAGQ01**	**JGH3225FAGQ02**	—	—
		Electronic Trip LS			
250	—	**JGH325033GQ01**	**JGH325033GQ02**	—	—
		Electronic Trip LSI			
250	—	**JGH325032GQ01**	**JGH325032GQ02**	—	—
		Electronic Trip LSG			
250	—	**JGH325035GQ01**	**JGH325035GQ02**	—	—
		Electronic Trip LSIG			
250	—	**JGH325036GQ01**	**JGH325036GQ02**	—	—

Series G HMCP

Ampere Rating	Motor Circuit Protector with Line Side Mounted Current Limiter	Breaker with Load Side Mounted Current Limiter
250	**HMCPJ250D5LQ01**	**HMCPJ250D5LQ02**
250	**HMCPJ250F5LQ01**	**HMCPJ250F5LQ02**
250	**HMCPJ250G5LQ01**	**HMCPJ250G5LQ02**
250	**HMCPJ250J5LQ01**	**HMCPJ250J5LQ02**
250	**HMCPJ250K5LQ01**	**HMCPJ250K5LQ02**
250	**HMCPJ250L5LQ01**	**HMCPJ250L5LQ02**

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	Metric Wire Range mm^2	AWG Wire Range/ Number of Conductors	Catalog Number
Standard Pressure Type Terminals					
250	Aluminum	Cu/Al	10–185	#8–350 (1)	**TA250FJ** ③

Notes

① Two interphase barriers provided, mounted on line end of limiter, catalog number **FJIPBK**.

② Four interphase barriers provided, (2) line end of breaker, (2) load end of limiter.

③ Line and load terminals included with products listed above.

Technical Data and Specifications

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
JGH…Q	240 V/200 kA	48.60	2.47
JGH…Q	480 V/200 kA	48.60	2.47
JGH…Q	600 V/200 kA	48.60	2.47

Dimensions and Weights

Approximate Dimensions in Inches (mm)

Assembled Breaker and Current Limiting Module

Frame	Height	Width	Depth	Weight in lbs (kg)
JG + limiter	13.06 (331.7)	4.13 (104.9)	3.44 (87.4)	9.87 (4.48)
HMCP	13.06 (331.7)	4.13 (104.9)	3.44 (87.4)	9.87 (4.48)

JG-Frame With Current Limiter Module



High Instantaneous Circuit Breaker for Selective Coordination

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	
Product Selection	**V4-T2-102**
Technical Data and Specifications	**V4-T2-103**
Dimensions	**V4-T2-103**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

High Instantaneous Circuit Breaker for Selective Coordination

Product Description

Eaton's Electrical Sector introduces new high-magnetic withstand molded case circuit breakers, specifically designed for critical operations and selective coordination requirements. The high-magnetic withstand LHH and NHH frames continue the legacy of circuit breaker innovation for which Eaton is recognized throughout the world. The LHH and NHH breakers are equipped with 125 to 400 ampere trip units with high-magnetic capability. This design enables the breakers to withstand up to 90 times rated current before opening under short-circuit conditions.

The LHH and NHH circuit breakers incorporate a higher level of instantaneous pickup, thus allowing for higher current levels of selective coordination. Standard molded case circuit breakers typically are furnished with a magnetic pickup or electronic instantaneous adjustment or instantaneous override set at 10 times (10x) the continuous trip rating.

Features, Benefits and Functions

Eaton's new LHH and NHH molded case circuit breakers are furnished with a higher level of magnetic pickup or electronic instantaneous settings as indicated in table on **Page V4-T2-103**. These higher levels of magnetic pickup and electronic instantaneous values in turn allow the system designer to obtain selective coordination at fault current levels up to these higher ratings. Greater values of selective coordination are available based on manufacturer tested combinations using the LHH and NHH as line-side breakers and standard breakers as load-side devices. Refer to IA01200002E to determine the maximum fault values that selective coordination achieves. When the line-side and load-side molded case circuit breaker trip ratings are chosen to coordinate in the overload range, they also can be selectively coordinated in the fault range up to the values listed in the table on **Page V4-T2-103** or IA01200002E. For overcurrents protected by circuit breakers on the load-side of the LHH or NHH, only the effected load-side circuit breaker will open, while the line-side LHH and/or NHH circuit breakers remain closed, thus providing continuity of power to the other critical loads supplied by the LHH or NHH circuit breakers.

Benefits of Using the LHH and NHH Molded Case Circuit Breakers

Customer expectations and codes are driving product development to protect customers' critical operations. NEC® 2005 and 2008 requires circuits with elevators, emergency systems, legally required standby systems, health care essential systems and critical operation power systems to be selectively coordinated. Simply stated, only the closest protective device directly protecting the circuit having an overcurrent (overload or fault) condition should open.

All other overcurrent protective devices within these systems shall remain closed. Similarly, backup power system designs of a critical nature that are not code mandated may also require overcurrent protective devices to be selectively coordinated as much as practicable to provide a higher level of uptime.

Proven Technology and Performance

The LHH is based on the Series G L-Frame circuit breaker, sharing the same small footprint and field-fit accessories as the L-Frame breaker. The NHH is based on the Series G N-Frame circuit breaker and shares the same footprint and accessories as the N-Frame breaker. NHH accessories must be factory installed.

The LHH incorporates a thermal-magnetic trip unit with fixed thermal and fixed magnetic settings. The NHH has an OPTIM™ electronic trip unit with LSI adjustment capabilities. The instantaneous setting is adjustable from 1000–4000 A or may be turned off to default to the frame override of 14,000 A. A hand-held OPTIMizer must be used with the NHH to adjust short-time delay and instantaneous, however, the long delay pickup is fixed and cannot be adjusted.

The LHH and NHH breakers are available in Eaton's panelboards and switchboards.

Standards and Certifications

- UL
- CSA

Listed

Product Selection

LHH

LHH and NHH Catalog Numbers

Ampere Rating	Thermal-Magnetic Trip Unit LHH Frame	LSI Electronic Trip Unit NHH Frame
125	**LHH3125FFG**	—
150	**LHH3150FFG**	**NHH3150T52X15**
175	**LHH3175FFG**	**NHH3175T52X15**
200	**LHH3200FFG**	**NHH3200T52X15**
225	**LHH3225FFG**	**NHH3225T52X15**
250	**LHH3250FFG**	**NHH3250T52X15**
300	**LHH3300FFG**	**NHH3300T52X15**
350	**LHH3350FFG**	**NHH3350T52X15**
400	**LHH3400FFG**	—

Technical Data and Specifications

- Three-pole
- 65 kAIC at 480 Vac
- 125–400 ampere LHH
- 150–350 ampere NHH
- Trip units:
- LHH—thermal-magnetic
- NHH—LSI electronic trip unit
- No rating plugs required
- Factory-sealed breakers
- LHH uses same internal and external accessories as standard Series G L-Frame circuit breaker
- NHH uses same internal and external accessories as standard Series G N-Frame circuit breaker

LHH and NHH Electrical Characteristics

Short-Circuit Current Ratings (kA rms) AC 50–60 Hz

Description	Breaker Type LHH	NHH
Max. rated current (amperes)	400	350
NEMA UL 489		
240 Vac	100	100
480 Vac	65	65
600 Vac	35	35
250 Vac	42	—
IEC 60947-2		
220 Vac	100	100
415 Vac	70	70
690 Vac	25	25
125/250 Vdc	22	—
Number of poles	3	3
Ampere range	125–400 A	150–350 A

Continuous Current Ratings

Continuous Current Rating (I_r)	Magnetic Trip Point	Continuous Current Multiplier	Instantaneous Trip Point	Continuous Current Multiplier	Short Delay Pickup
125 A	2500 A	20x	—	—	—
150 A	2500 A	16x	14,000 A	93x	225–1200 A
175 A	4000 A	22x	14,000 A	80x	260–1400 A
200 A	4000 A	20x	14,000 A	70x	300–1600 A
225 A	6000 A	26x	14,000 A	62x	338–1800 A
250 A	6000 A	24x	14,000 A	56x	375–2000 A
300 A	6000 A	20x	14,000 A	47x	450–2400 A
350 A	6000 A	17x	14,000 A	40x	525–2800 A
400 A	6000 A	15x	—	—	—

Dimensions

Approximate Dimensions in Inches (mm)

Dimensions

Description	Height	Width	Depth	Weight in Lbs (kg)
LHH	10.13 (257.3)	5.48 (139.2)	4.09 (103.9)	12.36 (5.6)
NHH	16.00 (406.4)	8.25 (209.5)	5.50 (139.7)	46.80 (21.2)

L-Frame



N-Frame



Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	
Internal Accessories	**V4-T2-106**
External Accessories and Test Kit	**V4-T2-107**
Accessories	**V4-T2-109**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Special Features and Accessories

Eaton's molded case circuit breakers are designed to provide circuit protection for low voltage distribution systems. They are described by NEMA as, "... a device for closing and interrupting a circuit between separable contacts under both normal and abnormal conditions," and furthermore as, "... a breaker assembled as an integral unit in a supporting and enclosing housing of insulating material." The National Electrical Code (NEC) describes them as, "A device designed to open and close a circuit by non-automatic means, and to open the circuit automatically on a predetermined overload of current, without injury to itself when properly applied within its rating."

So designed, Eaton circuit breakers protect conductors against overloads and conductors and connected apparatus, such as motors and motor starters, against short circuits.

In low voltage distribution systems, there are many varied applications of molded case circuit breakers. Eaton offers the most comprehensive family of molded case circuit breakers in the industry.

This section of circuit breakers includes:

- Thermal-magnetic trip breakers
- Electronic rms trip breakers
- Molded case switches
- Motor circuit protectors
- Current limiting breakers
- Special application breakers

Modified Breakers

Eaton breakers can be ordered with internal accessories installed. These modified breakers will be subject to an addition charge.

Special Calibration

Special non-UL listed calibrations are available for certain ambient temperatures other than 40 °C and for frequencies other than 50/60 Hz or DC. Reduced interrupting ratings will apply for 400 Hz applications.

- Add suffix H01 to breaker catalog number for 400 Hz rating

50 °C Calibration

Note: Breakers equipped with electronic trip units can operate reliably in ambient temperatures of 50 °C. Add suffix "V3" to NG MCCBs to remove standard 40 °C labeling.

Add suffix "V" to catalog number for complete thermal magnetic breaker when ordering listed ampere ratings for breakers to be used in 50 °C ambients. 50 °C ambient MCCBs are not UL listed.

Contact Eaton for availability.

Calibrations and Treatment

Description	Frame EG	JG	LG	NG	RG
Special calibration	■	■	■	■	■
Moisture-fungus treatment	■	■	■	■	■

Moisture-Fungus Treatment

All Eaton circuit breaker cases are molded from glass-polyester, which does not support the growth of fungus. Any parts that are susceptible to the growth of fungus will require special treatment.

Order by description.

- Add suffix J01 to breaker catalog number

Freeze-Tested Circuit Breakers

The circuit breakers may be ordered with freeze testing. This option uses special lubrication and mechanical operation is verified at –40 °C.

- Add suffix F01 to catalog number –57 °F, F02 –30 °F

Marine Applications

E- to R-Framed circuit breakers can be supplied to meet the following marine specifications:

- U.S. Coast Guard CFR 46; ABS—American Bureau of Shipping; IEEE 45; DNV; and Lloyds

These specifications generally require molded case circuit breakers to be supplied with 50 °C ambient, and plug-in adapter kits. When plug-in adapter kits are used, no terminals need be supplied (switchboard applications).

Circuit breakers can also be supplied to meet UL 489 Supplement SA (Marine use) and UL 489 Supplement SB (Naval Use).

UL 489 Supplement SA applies to vessels over 65 feet (19.8m) in length.

Requirements include 40 °C ambient calibration, special labeling, and no use of aluminum conductors or terminals. (No 50 °C.)

- Add suffix H08

Or you can choose to add 50°C ambient but then there is no "UL" mark.

- Add suffix VH08

UL 489 Supplement SB requires partial 50 °C ambient calibration, vibration testing, special nameplating and no use of aluminum conductors or terminals. Eaton chooses to always fully calibrate to 50 °C ambient. ("Naval" labeled per UL but no "UL" mark due to 50 °C label.)

- Add suffix VH09

Certified Test Reports

Eaton breakers can be ordered with certified test reports at the time of order entry. Test report documents the thermal and magnetic or electronic tripping characteristics of the individual breaker. Breaker and test report must be ordered together. Add suffix 12 to breaker catalog number and enter separate line item on order for certified test report.

Standards and Certifications

Molded case circuit breakers are designed to conform with the following standards:

- Underwriters Laboratories Inc., Standard UL 489, molded case circuit breakers and circuit breaker enclosures
- National Electrical Manufacturers Association (NEMA) Standards Publication No. AB1-1993, molded case circuit breakers
- Australian Standard AS 2184, molded case circuit breakers
- British Standards Institution Standard BS 4752: Part 1, switchgear and control gear Part 1: circuit breakers
- Canadian Standards Association (CSA) Standard C22.2 No. 5, service entrance and branch circuit breakers
- International Electrotechnical Commission Recommendations IEC 60947-2, circuit breakers
- Japanese T-Mark Standard molded case circuit breakers
- South African Bureau of Standards, Standard SABS 156, Standard Specification for molded case circuit breakers
- Swiss Electro-Technical Association Standard SEV 157-1, safety regulations for circuit breakers
- Union Technique de l'Electricite Standard NF C 63-120, low voltage switchgear and control gear circuit breaker requirements
- Verband Deutscher Elektrotechniker (Association of German Electrical Engineers) Standard VDE 0660, low voltage switchgear and control gear, circuit breakers

Conformance with these standards satisfies most local and international codes, assuming user acceptability and simplified application.

Molded case circuit breakers equal or exceed Federal Specification Classification W-C-375b requirements for the particular class associated with the circuit breaker frame being considered.

Open breakers do not have service entrance ratings. Service entrance rating is part of the enclosure.

Listed

Internal Accessories

Alarm Lockout

The alarm switches operate when the circuit breaker is tripped by a short circuit or overcurrent, but also when it is tripped by a shunt trip or undervoltage release.

Auxiliary Switches

Auxiliary switches are used for signaling and control purposes. The various functions of the auxiliary switches (changeover) are shown on **Page V4-T2-108**.

Shunt Trips

The shunt trip is used for remote tripping.

The coil of the shunt trip is rated only for short-time operation.

It is not permissible with the circuit breaker open to apply a continuous opening command to the shunt trip in order to prevent the breaker from closing. This means that interlocking circuits with continuous commands may not be set up with shunt trips.

Undervoltage Releases

The circuit breaker cannot be closed until the undervoltage release is energized. If the release is not energized, the circuit breaker can only perform an idle switching operation.

Frequent idle switching actions should be avoided as they shorten the endurance of the circuit breaker.

Digitrip 310+ Electronic Trip Unit Accessories

Cause of Trip Display/Remote Mount Cause of Trip Display

The Cause of Trip Display can be field-installed on any Digitrip RMS 310+ trip unit. The device provides breaker information through an LCD screen, such as cause of trip, phrase current, ground current and low loads. The display is ideal for troubleshooting common trips such as ground fault, long delay, and instantaneous/short delay. The DIGIVIEW version will provide a local display at the breaker without additional wiring by connecting directly onto the trip unit. The DIGIVIEWR06 version has a 6 foot cable that allows users to mount the display on the outside of an enclosure door and connect to the trip unit that is contained inside the enclosure.

The DIGIVIEWR06 is NEMA 3R rated.

Cause of Trip Display/ Remote Mount Cause of Trip Display

Catalog Number
DIGIVIEW
DIGIVIEWR06

Cause of Trip LED Module

The Cause of Trip LED Module can be field-installed on any Digitrip RMS 310+ trip unit. The device provides a cause of trip indication via LED. The Cause of Trip LED Module connects directly onto the trip unit. When the breaker trips, the module indicates the cause of trip (long delay, short delay, instantaneous and ground) via LED indication. The module is reset after the breaker is reset.

Cause of Trip LED Module

Catalog Number
TRIP-LED

Electronic Portable Test Kit

The electronic portable test kit provides a means to complete field tests using secondary injection on all 310+ trip units. The same test kit is also capable of secondary injection testing on Magnum and Series NRX low voltage power circuit breakers' 520 and 1150 trip units.

Electronic Portable Test Kit

Catalog Number
MTST230V

Wire Seal

The wire seal can be used to secure the cover of the trip unit to prevent adjustments after settings are confirmed.

Wire Seal

Catalog Number
5108A03H01

External Accessories and Test Kit

External Accessories

Description	Fit Type	Frame EG	JG	LG	NG	RG
Non-padlockable handle block	Field	**EFHB**	—	—	**LKD4**	—
Padlockable handle block	Field	**EFPHB**	—	—	—	—
Padlockable handle block off-only	Field	**EFPHBOFF**	**FJPHBOFF**	**LBHPOFF**	—	—
Padlockable handle lock hasp	Field	**EFPLK**	**FJPHL**	**LPHL**	**PLK5**	**HLK6**
Padlockable handle lock hasp off-only	Field	**EFPHLOFF**	**FJPHLOFF**	**LPHLOFF**	**PLK55OFF**	**HLK6OFF**
Kirk key interlock kit ①②	Field	—	**KYKJG**	**KYKLG**	**KYK4**	**KYK6**
Castell key interlock kit ②③	Field	—	**CTKJG**	**CTKLG**	**CTK4**	**CTK6**
Slide bar interlock ④	Field	**EFSBI**	**FJSBI**	**LGSBI**	**SBK5**	—
Walking beam interlock ④	Three-pole	**EG3WBI**	**JG3WBI**	**LG3WBI**	**WBL5**	**WBL6**
	Four-pole	**EG4WBI**	**JG4WBI**	**LG4WBI**	**WBL5**	—
Electrical operator ⑤	120 Vac	**MOPEG240C**	**MOPJG120C**	**MOPLG120C**	**EOP5T07**	**EOP6T08K**
	240 Vac	**MOPEG240C**	**MOPJG240C**	**MOPLG240C**	**EOP5T11**	**EOP6T11K**
	24 Vdc	**MOPEG48D**	**MOPJG24D**	**MOPLG24D**	**EOP5T21**	—
	48 Vdc	**MOPEG48D**	—	—	**EOP5T22**	**EOP6T21K**
	125 Vdc	**MOPEG120C**	**MOPJG120C**	**MOPLG120C**	**EOP5T26**	—
	220 Vdc	—	**MOPJG240C**	**MOPLG240C**	—	—
	250 Vdc	—	**MOPJG240C**	**MOPLG240C**	—	—
Plug-in adapters	Three-pole	**PAD3E**	**PAD3J**	**PAD3L**	**PAD53**	—
	Four-pole	**PAD4E**	**PAD4J**	**PAD4L**	—	—
Wohner busbar adapter	Field top	**EG-BUS-T**	**JG-BUS-TB**	**LG-BUS-TB**	—	—
	Field bottom	**EG-BUS-B**	**JG-BUS-TB**	**LG-BUS-TB**	—	—

Series G MCCB Frames EG, JG, and LG to mount to the SASY 60 mm Wohner Classic System

- UL file # E197132
- Compact design
- UL508 tested and certified using Wohner system with Eaton breakers
- No line side wiring required
- Up to 630 A MCCB
- Reverse feed possible

Wohner Busbar Adapter

Wohner Busbar Adapters

Breaker Frame	Busbar Adapter	Connection Point
EG	**EG-BUS-T**	Top
EG	**EG-BUS-B**	Bottom
JG	**JG-BUS-TB**	Top or bottom
LG	**LG-BUS-TB**	Top or bottom

Notes

① Provision only.
② See **Page V4-T2-318** for bolt projection dimensions.
③ Castell bolt mounting hole must be 10 mm.
④ Requires two breakers.
⑤ Contact Eaton for availability of operators for EG- and NG-Frames before December 2004.

Accessory Configurations for EG–RG Circuit Breakers

2

Internal Accessory Configurations



□/U</ = Shunt Trip or Undervoltage Release
AUX = Auxiliary Switch
AS = Alarm Switch
¨ = For N-Frame Circuit Breakers Only
≠ = For R-Frame Circuit Breakers Only
¬ = For N and R-Frame Circuit Breakers Only

Contact Making by the Auxiliary and Alarm Switches as a Function of the Switching Position of the Circuit Breaker



Accessories

Field Fit Kit Catalog Numbers

Alarm Lockout

Description	Pole Location	Frame EG, JG and LG	NG	RG ①
Make/Break	Left	—	**A1L5LPK**	—
	Right	**ALM1M1BEPK** ②	**A1L5RPK**	**A1L6RPK**
2 Make/2 Break	Left	—	**A2L5LPK**	—
	Right	**ALM2M2BEPK** ③	**A2L5RPK**	**A2L6RPK**

Description	Pole Location	For Use in Frame	Contact Type	Catalog Number
Make/Break	Right	EG	Silver	**ALM1M1BEPK**
2 Make/ 2 Break	Right	EG	Silver	**ALM2M2BEPK**
Make/Break	Right	JG and LG	Silver	**ALM1M1BJPK**
2 Make/ 2 Break	Right	JG and LG	Silver	**ALM2M2BJPK**
Make/Break	Right	EG	Gold	**ALM1M1BEEPK**
2 Make/ 2 Break	Right	EG	Gold	**ALM2M2BEEPK**
Make/Break	Right	JG and LG	Gold	**ALM1M1BEJPK**
2 Make/ 2 Break	Right	JG and LG	Gold	**ALM2M2BEJPK**

Auxiliary Switch

Description	Pole Location	Frame EG, JG and LG	NG	RG ①
1A, 1B	Left	—	**A1X5PK**	—
	Right	**AUX1A1BPK**	**A1X5PK**	—
2A, 2B	Left	—	**A2X5PK**	—
	Right	**AUX2A2BPK**	**A2X5PK**	**A2X6RPK**
3A, 3B	Left	—	**A3X5LPK**	—
	Right	—	**A3X5RPK**	—
4A, 4B	Left	—	—	—
	Right	—	—	**A4X6RPK**

Description	Pole Location	For Use in Frame	Contact Type	Catalog Number
1A, 1B	Right	EG/JG/LG	Silver	**AUX1A1BPK**
2A, 2B	Right	EG/JG/LG	Silver	**AUX2A2BPK**
1A, 1B	Right	EG/JG/LG	Gold	**AUX1E1BPK**
2A, 2B	Right	EG/JG/LG	Gold	**AUX2E2BPK**

Auxiliary Switch/Alarm Lockout

Description	Pole Location	Frame EG, JG and LG	NG	RG ①
—	Left	—	**AA115LPK**	—
	Right	**AUXALRMEPK** ④	**AA115RPK**	—

Description	Pole Location	For Use in Frame	Contact Type	Catalog Number
1A/1B & 1M/1B	Right	EG	Silver	**AUXALRMEPK**
1A/1B & 1M/1B	Right	JG and LG	Silver	**AUXALRMJPK**
1A/1B & 1M/1B	Right	EG	Gold	**AUXALRMEEPK**
1A/1B & 1M/1B	Right	JG and LG	Gold	**AUXALRMEJPK**

Notes

① All accessories mount in the RH cavity which will accept one each of shunt trip, UVR, auxiliary switch and alarm switch.
② Part number for JG and LG is ALM1M1BJPK.
③ Part number for JG and LG is ALM2M2BJPK.
④ Part number for JG and LG is AUXALRMJPK.

2

Shunt Trip—Standard



Shunt Trip—Standard

Description	Pole Location	Frame EG, JG and LG ①	NG	RG ②
48–60 Vac	Left	**SNT4860CPK**	**SNT5LP05K**	—
	Right	—	—	**SNT6P05K**
110–240 Vac	Left	**SNT120CPK**	**SNT5LP11K**	—
	Right	—	—	**SNT6P11K**
380–600 Vac	Left	**SNT480CPK** ③	—	—
	Right	—	—	—
220–250 Vdc or 380–440 Vac		—	**SNT5LP14K**	**SNT6P14K**
480–600 Vac		—	**SNT5LP18K**	**SNT6P18K**
12 Vdc	Left	**SNT012CPK**	—	—
	Right	—	—	—
24 Vac/dc	Left	**SNT024CPK**	**SNT5LP03K**	—
	Right	—	—	**SNT6P03K**
48–60 Vdc	Left	**SNT4860CPK**	**SNT5LP23K**	—
	Right	—	—	**SNT6P23K**
110–125 Vdc	Left	**SNT125DPK**	**SNT5LP26K**	—
	Right	—	—	**SNT6P26K**
250 Vdc	Left	**SNT250DPK**	—	—
	Right	—	—	—

Shunt Trip—Low Energy

Description	Pole Location	Frame EG, JG and LG	NG	RG ②
—	Left	—	**LST5LPK**	—
	Right	—	—	**LST6RPK**

Undervoltage Release Mechanism

Description	Pole Location	Frame EG, JG and LG ①	NG	RG ②
110–127 Vac	Left	**UVR120APK**	**UVH5LP08K**	—
	Right	—	—	**UVH6RP08K**
208–240 Vac	Left	**UVR240APK**	**UVH5LP11K**	—
	Right	—	—	**UVH6RP11K**
24 Vdc	Left	**UVR024DPK**	**UVH5LP21K** ④	—
	Right	—	—	**UVH6RP21K** ④
24 Vac	Left	**UVR024APK**	**UVH5LP21K** ④	—
	Right	—	—	**UVH6RP21K** ④
48–60 Vdc	Left	**UVR048DPK**	**UVH5LP23K**	—
	Right	—	—	**UVH6RP23K**
48–60 Vac	Left	**UVR048APK**	**UVH5LP05K**	—
	Right	—	—	**UVH6RP05K**
120 Vdc	Left	**UVR125DPK**	**UVH5LP26K**	—
	Right	—	—	**UVH6RP26K**
220–250 Vdc	Left	**UVR250DPK**	**UVH5LP28K**	—
	Right	—	—	**UVH6RP28K**
380–500 Vac	Left	**UVR480APK**	**UVH5LP29K**	—
	Right	—	—	**UVH6RP29K**
525–600 Vac	Left	**UVR600APK**	—	—
	Right	—	—	—
12 Vdc	Left	—	**UVH5LP20K**	—
	Right	—	—	**UVH6RP20K**
12 Vac	Left	—	**UVH5LP02K**	—
	Right	—	—	**UVH6RP02K**

Notes

① LH cavity not available for EG frame with earth leakage module.
② All accessories mount in the RH cavity which will accept one each of shunt trip, UVR, auxiliary switch and alarm switch.
③ 380–600 Vdc, 50/60 Hz.
④ 24 Vdc only use UVH5LP03K (NG) UVH6RP03K (RG) for 24 Vac.

Technical Data and Specifications

Note: Gold-plated contacts are well suited for switching low voltages and currents. Lead wires on accessories containing gold-plated contacts are marked with a yellow stripe.

Series G Gold Contact Accessory Switch Electrical Ratings

Max. Voltage (Ue)	Frequency	Max. Current (I_n)	Dielectric Withstand Voltage (UI)
125 V	50/60 Hz	0.1 A	2200 V
30 V	DC	0.25 A	2200 V
5 V	DC	5 mA	2200 V

Series G Silver Contact Accessory Switch Electrical Ratings

Max. Voltage (Ue)	Frequency	Max. Current (I_n)	Dielectric Withstand Voltage (UI)
600 V	50/60 Hz	2 A	2200 V
125/250 V	50/60 Hz	5 A	2200 V
125 V	DC	1 A	2200 V

Series GJ Frame: Terminal Extension Kits

	Extension Orientation			
	Edgewise	Right Angle	Spreader	Straight
Three-pole	FJTEE3	FJTER3	FJTEW3	FJTES3
Four-pole	FJTEE4	FJTER4	FJTEW4	FJTES4

Series G Motor Operators

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	
Features, Benefits and Functions	**V4-T2-113**
Standards and Certifications	**V4-T2-113**
Product Selection	**V4-T2-113**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	**V4-T2-115**

Motor Operators

Product Description

Eaton's motor operator mechanism enables local and remote ON, OFF and reset switching of a circuit breaker. The motor operator is mounted on the circuit breaker cover within the dimensions of the circuit breaker.

The robust motor operators offer various voltages to maximize customer flexibility. Standard load transfer switching can be accomplished through the use of two circuit breakers fitted with motor operators and a mechanical interlock.

Features, Benefits and Functions

The motor operator provides special features for ease of customer use and status indication.

- The motor operator allows the circuit breaker to be opened, closed or reset remotely
- The motor operator contains a motor connected to a cam drive mechanism. The cam drives a slide mechanism to operate the circuit breaker handle
- Internal limit switches and relays are used to control motor operation to prevent overdriving the circuit breaker handle and motor overload conditions
- A key is provided to manually operate the circuit breaker
- A special pull-out locking mechanism provides a method for padlocking the circuit breaker handle in the OFF position
- The locking device will accept three padlock shackles with a maximum diameter of 1/4-inch (6.4 mm) each
- The cover provides visual status of the circuit breaker: ON, OFF or TRIPPED. A PUSH-TO-TRIP button allows the user to manually trip the breaker



Standards and Certifications

The motor operators are UL and CSA listed, and CE marked.

Listed

Product Selection

Motor Operators

Frame	Voltage	Frequency	Inrush Current	Catalog Number
Series G E-Frame	100–240 Vac	50/60 Hz	1A	**MOPEG240C**
	100–220 Vdc	DC	1A	**MOPEG240C**
	24/48 Vdc	DC	3A	**MOPEG48D**
Series C F-Frame	208–240 Vac	50/60 Hz	1A	**MOPFD240C**
	110–127 Vac	50/60 Hz	1A	**MOPFD120C**
	220–250 Vdc	DC	1A	**MOPFD240C**
	110–125 Vdc	DC	1A	**MOPFD120C**
	24 Vdc	DC	3A	**MOPFD24D**
Series G J-Frame	208–240 Vac	50/60 Hz	1A	**MOPJG240C**
	110–127 Vac	50/60 Hz	1A	**MOPJG120C**
	220–250 Vdc	DC	1A	**MOPJG240C**
	110–125 Vdc	DC	1A	**MOPJG120C**
	24 Vdc	DC	3A	**MOPJG24D**
Series G L-Frame	208–240 Vac	50/60 Hz	2A	**MOPLG240C**
	110–127 Vac	50/60 Hz	2A	**MOPLG120C**
	220–250 Vdc	DC	2A	**MOPLG240C**
	110–125 Vdc	DC	2A	**MOPLG120C**
	24 Vdc	DC	6A	**MOPLG24D**

LG Breaker with Plug-In Block



Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks Drawout Cassette	**V4-T2-115**

Plug-In Blocks

Product Description

Plug-in adapters simplify installation and front removal of circuit breakers. Plug-ins are available for rear connection applications on three- and four-pole circuit breakers. Trip on drawout interlock kits are included. Stabs for EG, JG and LG plug-ins rotate 90 ° for flexible installation. Use terminal shields for IP30 protection.

Product Selection

Plug-In Blocks

Breaker Frame	Number of Poles	Catalog Number
EG-, JG- and LG-Frame Plug-In Blocks		
EG	3	**PAD3E**
EG	4	**PAD4E**
JG	3	**PAD3J**
JG	4	**PAD4J**
LG	4	**PAD4L**
Trip-On Drawout Interlock Kit ①		
EG	3, 4	**PIILEG**
JG	3, 4	**PIILJG**
LG	3, 4	**PIILLG**
Terminal Shields IP30		
EG	3	**EFTS3K**
EG	4	**EFTS4K**
JG	3	**FJTS3K**
JG	4	**FJTS4K**
LG	3	**LTS3K**
LG	4	**LTS4K**

Note

① Included with plug-in block. Trips the breaker when breaker is removed from plug-in block.

Drawout Cassettes

Contents

Description	*Page*
EG-Frame (15–125 Amperes)	**V4-T2-15**
JG-Frame (63–250 Amperes)	**V4-T2-29**
LG-Frame (250–630 Amperes)	**V4-T2-47**
NG-Frame (320–1200 Amperes)	**V4-T2-65**
RG-Frame (800–2500 Amperes)	**V4-T2-74**
Motor Circuit Protectors (MCP)	**V4-T2-85**
Motor Protector Circuit Breakers (MPCB)	**V4-T2-89**
30 mA Ground Fault (Earth Leakage) Module	**V4-T2-92**
Current Limiting Circuit Breaker Module	**V4-T2-96**
High Instantaneous Circuit Breaker for Selective Coordination	**V4-T2-101**
Special Features and Accessories	**V4-T2-104**
Motor Operators	**V4-T2-112**
Plug-In Blocks	**V4-T2-114**
Drawout Cassette	

Drawout Cassette

Product Description

The drawout cassette is available for use with JG, LG and NG, three- and four-pole breakers. The cassettes consist of two separate components: the movable mechanism, which attaches to the breaker, and the stationary mechanism, which houses in the cassette. For the JG, LG and NG drawout cassettes, all necessary parts for installation are included in the one catalog number.

Features

Features of the drawout cassettes for the JG, LG and NG include:

- Trip on drawout—breaker will trip if it is in the ON position when withdrawn from the cassette
- Secondary terminal block—the drawout cassettes include a secondary terminal block for easier access when wiring low voltage accessories, including shunts and undervoltage releases

The drawout mechanism has three primary positions:

- Connected—the breaker is fully connected to the primary stabs and secondary contacts
- Disconnected—both the primary stabs and the secondary contacts are disconnected
- Withdraw—the breaker can be removed from the cassette

Product Selection

JG Drawout Cassette

LG Drawout Cassette

JG, LG and NG Drawout Cassettes

Breaker Frame	Number of Poles	Catalog Number
JG	3	**JG3DOM**
	4	**JG4DOM**
LG	3	**LG3DOM**
	4	**LG4DOM**
NG	3	**NG3DOM**
	4	**NG4DOM**

Molded Case Circuit Breaker Product Family

Contents

Description	*Page*
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Learn Online Drawings Online

Product Overview

Eaton's molded case circuit breakers are designed to provide circuit protection for low voltage distribution systems. They are described by NEMA as, "... a device for closing and interrupting a circuit between separable contacts under both normal and abnormal conditions," and furthermore as, "... a breaker assembled as an integral unit in a supporting and enclosing housing of insulating material." The National Electrical Code (NEC) describes them as, "A device designed to open and close a circuit by non-automatic means, and to open the circuit automatically on a predetermined overload of current, without injury to itself when properly applied within its rating."

So designed, Eaton circuit breakers protect conductors against overloads and conductors and connected apparatus, such as motors and motor starters, against short circuits.

In low voltage distribution systems, there are many varied applications of molded case circuit breakers.

Eaton offers the most comprehensive family of molded case circuit breakers in the industry.

This section of circuit breakers includes:

- Thermal-magnetic trip breakers
- Electronic rms trip breakers
- Molded case switches
- Motor circuit protectors
- Current limiting breakers
- Special application breakers

Modified Breakers

Eaton breakers can be ordered with internal accessories installed. These modified breakers will be subject to an addition charge.

Special Calibration

Special non-UL-listed calibrations are available for certain ambient temperatures other than 40 °C and for frequencies other than 50/60 Hz or DC. Reduced interrupting ratings will apply for 400 Hz applications.

50 °C Calibration

Add suffix **V** to catalog Number for complete breaker, listed above, when ordering listed ampere ratings for breakers to be used in 50 °C ambients. (No UL label.)

Moisture-Fungus Treatment

All circuit breaker cases are molded from glass-polyester which does not support the growth of fungus. Any parts which are susceptible to the growth of fungus will require special treatment.

Freeze-Tested Circuit Breakers

The circuit breakers may be ordered with freeze testing. This option uses special lubrication and mechanical operation is verified at –40 °C.

Marine Applications

E- to R-Framed circuit breakers can be supplied to meet the following marine specifications:

- U.S. Coast Guard CFR 46; ABS—American Bureau of Shipping; IEEE 45; DNV; Lloyds; and ABS/NVR

These specifications generally require molded case circuit breakers to be supplied with 50 °C ambient, and plug-in adapter kits. When plug-in adapter kits are used, no terminals need be supplied (switchboard applications).

Circuit breakers can also be supplied to meet UL 489 Supplement SA (Marine use) and UL 489 Supplement SB (Naval Use).

UL 489 Supplement SA applies to vessels over 65 feet (19.8 m) in length. Requirements include 40 °C ambient calibration, special labeling, and no use of aluminum conductors or terminals. (No 50 °C.)

- Suffix H08

Or you can choose to add 50 °C ambient but then there is no "UL" mark.

- Suffix VH08

UL 489 Supplement SB requires partial 50 °C ambient calibration, vibration testing, special nameplating and no use of aluminum conductors or terminals. Eaton chooses to always fully calibrate to 50 °C ambient. ("Naval" labeled per UL, and UL now allows 50 °C label here.)

- Suffix VH09

Certified Test Reports

Eaton breakers can be ordered with certified test reports at the time of order entry. Test report documents the thermal and magnetic or electronic tripping characteristics of the individual breaker. Breaker and test report must be ordered together. Add suffix 12 to breaker catalog number and enter separate line item on order for certified test report.

Standards and Certifications

Molded case circuit breakers are designed to conform with the following standards:

- Underwriters Laboratories Inc., Standard UL 489, molded case circuit breakers and circuit breaker enclosures
- National Electrical Manufacturers Association (NEMA) Standards Publication No. AB1-1993, molded case circuit breakers
- Australian Standard AS 2184, molded case circuit breakers
- British Standards Institution Standard BS 4752: Part 1, switchgear and control gear Part 1: circuit breakers
- Canadian Standards Association (CSA) Standard C22.2 No. 5, service entrance and branch circuit breakers
- International Electrotechnical Commission Recommendations IEC 60947-2, circuit breakers
- Japanese T-Mark Standard molded case circuit breakers
- South African Bureau of Standards, Standard SABS 156, Standard Specification for molded case circuit breakers
- Swiss Electro-Technical Association Standard SEV 157-1, safety regulations for circuit breakers
- Union Technique de l'Electricite Standard NF C 63-120, low voltage switchgear and control gear circuit breaker requirements
- Verband Deutscher Elektrotechniker (Association of German Electrical Engineers) Standard VDE 0660, low voltage switchgear and control gear, circuit breakers

Conformance with these standards satisfies most local and international codes, assuming user acceptability and simplified application.

Molded case circuit breakers equal or exceed Federal Specification Classification W-C-375b requirements for the particular class associated with the circuit breaker frame being considered.

Open breakers do not have service entrance ratings. Service entrance rating is part of the enclosure.

Listed

Quick Reference

Industrial Circuit Breakers

2

G-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125 ③	250	Page Number
GHB	15–100	1	120	125	N.I.T.U.	11a	65	—	—	—	—	—	14	—	**V4-T2-126**
GHB	15–100	2, 3	240	125/250	N.I.T.U.	11a10b, 11b	—	—	65	—	—	—	—	14	**V4-T2-126**
GHB	15–100	1	277	125	N.I.T.U.	12b, 14b	—	—	—	14	—	—	14	—	**V4-T2-126**
GHB	15–100	2, 3	480Y/277	125/250	N.I.T.U.	15b	—	—	—	14	14	—	—	14	**V4-T2-126**
HGHB	15–30	1	277	125	N.I.T.U.	12c, 13a, 13b	65	—	—	25	—	—	14	—	**V4-T2-126**
GHBS	15–30	1, 2	480Y/277	—	—	—	65	65	—	14	—	—	—	—	**V4-T1-34**
GBHS	15–20	1, 2	600Y/347	—	N.I.T.U.	—	—	—	—	—	—	10	—	—	**V4-T1-34**
GDB	15–50	2	480	125/250	N.I.T.U.	—	—	—	—	—	14	—	—	10	**V4-T2-124**
GDB	15–100	3	480	250	N.I.T.U.	—	—	—	—	—	14	—	—	10	**V4-T2-124**
GD	15–50	2	480	125/250	N.I.T.U.	13b	—	—	65	—	14	—	—	10	**V4-T2-123**
GD	15–100	3	480	250	N.I.T.U.	13b	—	—	65	—	22	—	—	10	**V4-T2-123**
GHC	15–100	1	120	125	N.I.T.U.	12c, 13a	65	—	—	—	—	—	14	—	**V4-T2-131**
GHC	15–100	2, 3	240	125/250	N.I.T.U.	13b	—	—	65		—	—	—	1	**V4-T2-131**
GHC	15–100	1	277	125	N.I.T.U.	12c, 13a	—	—	—	14	—	—	14	—	**V4-T2-131**
GHC	15–100	2, 3	480Y/277	125/250	N.I.T.U.	13b	—	—	—	14	14	—	—	14	**V4-T2-131**
HGHC	15–30	1	277	125	N.I.T.U.	—	65	—	—	25	—	—	14	—	**V4-T2-131**

Notes

① N.I.T.U. is non-interchangeable trip unit and I.T.U. is interchangeable trip unit.

② Two-pole circuit breaker, or two poles of three-pole circuit breaker at 250 Vdc.

③ Single-pole breakers can be applied in DC systems up to 70 A.

F-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125	250	Page Number
EDB	100–225	2, 3	240	125	N.I.T.U.	—	—	—	22	—	—	—	10	—	**V4-T2-135**
EDS	100–225	2, 3	240	125	N.I.T.U.	—	—	—	42	—	—	—	10	—	**V4-T2-135**
ED	15–225	2, 3	240	125	N.I.T.U.	12b	—	—	65	—	—	—	10	—	**V4-T2-135**
EDH	100–225	2, 3	240	125	N.I.T.U.	14b	—	—	100	—	—	—	10	—	**V4-T2-135**
EDC	100–225	2, 3	240	125	N.I.T.U.	1	—	—	200	—	—	—	10	—	**V4-T2-135**
EHD	15–100	1	277	125	N.I.T.U.	13a	—	—	—	14	—	—	10	—	**V4-T2-135**
EHD	15–100	2, 3	480	250	N.I.T.U.	13b	—	—	18	—	14	—	—	10	**V4-T2-135**
FDB	15–150	2, 3	600	250	N.I.T.U.	18a	—	—	18	—	14	14	—	10	**V4-T2-135**
FDB	15–150	4	600	250	N.I.T.U.	③	—	—	18	—	14	14	—	10	**V4-T2-135**
FD	15–150	1	277	125	N.I.T.U.	13a	—	—	—	35	—	—	10	—	**V4-T2-135**
FD	15–225	2, 3	600	250	N.I.T.U.	22a	—	—	65	—	35	18	—	10	**V4-T2-135**
FD	15–225	4	600	250	N.I.T.U.	③	—	—	65	—	35	18	—	10	**V4-T2-135**
FDE	15–225	3	600	—	N.I.T.U.	—	—	—	65	—	35	18	—	—	**V4-T2-135**
HFD	15–150	1	277	125	N.I.T.U.	13a	—	—	—	65	—	—	10	—	**V4-T2-135**
HFD	15–225	2,3	600	250	N.I.T.U.	22a	—	—	100	—	65	25	—	22	**V4-T2-135**
HFD	15–225	4	600	250	N.I.T.U.	③	—	—	100	—	65	25	—	22	**V4-T2-135**
HFDE	15–225	3	600	—	N.I.T.U.	—	—	—	100	—	65	25	—	—	**V4-T2-135**
FDC ④	15–225	2, 3	600	250	N.I.T.U.	24a	—	—	200	—	100	35	—	22	**V4-T2-135**
FDC ④	15–225	4	600	250	N.I.T.U.	③	—	—	200	—	100	35	—	22	**V4-T2-135**
FDCE ④⑤	15–225	3	600	—	N.I.T.U.	—	—	—	200	—	100	25	—	—	**V4-T2-135**

Notes

① N.I.T.U. is non-interchangeable trip unit and I.T.U. is interchangeable trip unit.
② Two-pole circuit breaker, or two poles of three-pole circuit breaker at 250 Vdc.
③ Not defined in W-C-375b.
④ Current limiting.
⑤ Check with Eaton for availability.

J-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125	250	Page Number
JDB	70–250	2, 3	600	250	N.I.T.U.	22a	—	—	65	—	35	18	—	10	**V4-T2-156**
JD	70–250	2, 3, 4	600	250	I.T.U.	22a	—	—	65	—	35	18	—	10	**V4-T2-155**
HJD	70–250	2, 3, 4	600	250	I.T.U.	22a	—	—	100	—	65	25	—	22	**V4-T2-155**
JDC ③	70–250	2, 3, 4	600	250	I.T.U.	22a	—	—	200	—	100	35	—	22	**V4-T2-155**

K-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125	250	Page Number
DK	250–400	2, 3	240	250	N.I.T.U.	14b	—	—	65	—	—	—	—	10	**V4-T2-167**
KDB	100–400	2, 3	600	250	N.I.T.U.	23a	—	—	65	—	35	25	—	10	**V4-T2-167**
KD	100–400	2, 3, 4	600	250	I.T.U.	23a	—	—	65	—	35	25	—	10	**V4-T2-164, V4-T2-165, V4-T2-169, V4-T2-172**
CKD	100–400	2, 3, 4	600	250	I.T.U.	23a	—	—	65	—	35	25	—	—	**V4-T2-166, V4-T2-175, V4-T2-177**
HKD	100–400	2, 3, 4	600	250	I.T.U.	23a	—	—	100	—	65	35	—	22	**V4-T2-164, V4-T2-165, V4-T2-169, V4-T2-172**
CHKD	100–400	2, 3, 4	600	250	I.T.U.	23a	—	—	100	—	65	35	—	—	**V4-T2-166, V4-T2-175, V4-T2-177**
KDC ③	100–400	2, 3, 4	600	250	I.T.U.	23a	—	—	200	—	100	65	—	22	**V4-T2-164, V4-T2-165, V4-T2-169, V4-T2-172**

L-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125	250	Page Number
LDB	300–600	2, 3	600	250	N.I.T.U.	23a	—	—	65	—	35	25	—	22	**V4-T2-190**
LD	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	65	—	35	25	—	22	**V4-T2-188, V4-T2-189, V4-T2-194**
CLD	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	65	—	35	25	—	—	**V4-T2-190, V4-T2-200**
HLD	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	100	—	65	35	—	25	**V4-T2-188, V4-T2-189, V4-T2-194**
CHLD	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	100	—	65	35	—	—	**V4-T2-190, V4-T2-200**
LDC ③	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	200	—	100	50	—	30	**V4-T2-188, V4-T2-189, V4-T2-196**
CLDC ③	300–600	2, 3, 4	600	250	I.T.U.	23a	—	—	200	—	100	50	—	30	**V4-T2-190, V4-T2-202**

M-Frame

Circuit Breaker Type	Continuous Ampere Rating at 40 °C	No. of Poles	Volts AC	Volts DC	Type of Trip ①	Federal Specification W-C-375b	UL Listed Interrupting Ratings (rms Symmetrical Amperes) AC (kA) 120	120/240	240	277	480	600	DC (kA) ② 125	250	Page Number
MDL	300–800	2, 3	600	250	I.T.U.	23a	—	—	65	—	50	25	—	22	**V4-T2-213, V4-T2-215**
CMDL	300–800	2, 3	600	250	I.T.U.	23a	—	—	65	—	50	25	—	—	**V4-T2-215**
HMDL	300–800	2, 3	600	250	I.T.U.	23a	—	—	100	—	65	35	—	25	**V4-T2-213, V4-T2-215**
CHMDL	300–800	2, 3	600	250	I.T.U.	23a	—	—	100	—	65	35	—	—	**V4-T2-215**

Notes

① N.I.T.U. is non-interchangeable trip unit and I.T.U. is interchangeable trip unit.

② Two-pole circuit breaker, or two poles of three-pole circuit breaker at 250 Vdc.

③ Current limiting.

Molded Case Circuit Breaker Product Family

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	
Catalog Number Selection	**V4-T2-122**
Technical Data and Specifications	**V4-T2-122**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

G-Frame (15–100 Amperes)

Product Description

- All two- and three-pole circuit breakers are of the common trip type. On all three-phase delta (240 V) Grounded B phase applications, refer to Eaton
- Single-pole circuit breakers, 15 and 20 amperes. Switching duty rated (SWD) for fluorescent lighting applications
- All G-Frame circuit breakers are suitable for reverse feed use
- HACR rated

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

Circuit Breaker/Frame

GD 3 100 K

Circuit Breaker Type	
GD	**HGHB**
GDB	**HGHC**
GHB	**GHBGFEP**
GHC	**GHCGFEP**
GHQ	

Number of Poles
1 = 1 pole
2 = 2 poles
3 = 3 poles

Trip Amperes		
015	**035**	**070**
020	**040**	**080**
024	**045**	**090**
030	**050**	**100**
	060	

Suffix	
K = Molded case switch	**J01**= Fungus proofed
D = Ring type terminals	**R01**= Shock tested
C = Steel collars	**F01**= Freeze tester
V = 122 °F (50 °C)	**HID**= High intensity discharge ①

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings

		Interrupting Capacity (kA Symmetrical Amperes)						
		Volts AC (50/60 Hz)					Volts DC	
Circuit Breaker Type	Number of Poles	120	240	277	480	480Y/277	125 ②	250 ③④
GDB	2, 3	—	—	—	14	—	—	10
GD	2	—	65	—	14	—	—	10
GD	3	—	65	—	22	—	—	10
GHQ	—	65	—	14	—	—	—	—
GHB	1	65	—	14	—	—	14	—
GHB	2, 3	—	65	—	—	14	14	—
HGHB	1	65	—	25	—	—	14	—
GHC	1	65	—	14	—	—	14	—
GHC	2, 3	—	65	—	—	14	14	—
HGHC	1	65	—	25	—	—	14	—

Terminal Types

For line and load-side. Terminals are UL listed as suitable for wire type and size given below.

Terminal Types

Circuit Breaker Amperes	Terminal Type Material	Screw Head Type	Wire Type	AWG Wire Range	Metric Wire Range (mm^2) ⑤
Standard					
15–20	Clamp (plated steel)	Slotted	Cu/Al	14–10	2.5–4
25–100	Pressure (aluminum body)	Slotted	Cu/Al	10–1/0	4–50
Optional—GD, GHB, GHC					
15–100	Pressure (steel body)	Slotted	Cu	14–3	—

Notes

① HID suffix only applies to the GHB and GHC single-pole, 15–20 A circuit breakers.
② Single-pole breakers can be applied in DC systems up to 70 A.
③ Time constant is 8 milliseconds minimum.
④ Two poles of three-pole circuit breaker.
⑤ Not UL listed sizes.

Typical G-Frame Circuit Breaker

Contents

Description	*Page*
Product Overview	V4-T2-116
Standards and Certifications	V4-T2-117
Quick Reference	V4-T2-118
G-Frame (15–100 Amperes)	V4-T2-121
F-Frame (10–225 Amperes)	V4-T2-135
J-Frame (70–250 Amperes)	V4-T2-153
K-Frame (70–400 Amperes)	V4-T2-161
L-Frame (125–600 Amperes)	V4-T2-185
M-Frame (300–800 Amperes)	V4-T2-211
N-Frame (400–1200 Amperes)	V4-T2-222
R-Frame (800–2500 Amperes)	V4-T2-237
Motor Circuit Protectors (MCP)	V4-T2-256
Motor Protection Circuit Breakers (MPCB)	V4-T2-267
Type ELC Current Limiter Attachment (Size 0–4)	V4-T2-269
Current Limiting Circuit Breaker Module	V4-T2-270
Internal Accessories	V4-T2-273
External Accessories	V4-T2-306

Type GD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (15–100 Amperes)

Product Description

- Cable in, cable out
- Includes mounting hardware and BMHE

Standards and Certifications

- UL/CSA

Listed

Product Selection

Type GD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C	480 Vac Maximum, 250 Vdc 14 kAIC at 480 Vac Includes Line and Load Terminals Two-Pole Catalog Number	22 kAIC at 480 Vac Three-Pole Catalog Number	Includes Binding Head Screws and Clamps 10–32 x 0.312 Three-Pole Catalog Number
15	GD2015	GD3015	GD3015D
20	GD2020	GD3020	GD3020D
25	GD2025	GD3025	GD3025D
30	GD2030	GD3030	GD3030D
35	GD2035	GD3035	GD3035D
40	GD2040	GD3040	GD3040D
45	GD2045	GD3045	GD3045D
50	GD2050	GD3050	GD3050D
60	—	GD3060	GD3060D
70	—	GD3070	GD3070D
80	—	GD3080	GD3080D
90	—	GD3090	GD3090D
100	—	GD3100	GD3100D

Type GDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C	480 Vac Maximum, 250 Vdc 14 kAIC at 480 Vac Includes Line and Load Terminals Two-Pole Catalog Number	Three-Pole Catalog Number
15	**GDB2015**	**GDB3015**
20	**GDB2020**	**GDB3020**
25	**GDB2025**	**GDB3025**
30	**GDB2030**	**GDB3030**
35	**GDB2035**	**GDB3035**
40	**GDB2040**	**GDB3040**
45	**GDB2045**	**GDB3045**
50	**GDB2050**	**GDB3050**
60	—	**GDB3060**
70	—	**GDB3070**
80	—	**GDB3080**
90	—	**GDB3090**
100	—	**GDB3100**

Type GD Molded Case Switches

Type GD Molded Case Switches—Three-Pole

Maximum Continuous Ampere Rating at 40 °C	480 Vac Maximum, 250 Vdc Catalog Number (Includes Line and Load Terminals)
60	**GD3060K**
60	**GD3060KC** ①
100	**GD3100K**
100	**GD3100KD** ②

Notes

① Includes line and load steel terminals.

② Includes binding head screws and clamps 10–32 x 0.312.

Molded case switches may open above 1300 amperes.

Dimensions

Approximate Dimensions in Inches (mm)

GD-Frame, Three-Pole

Front View



Side View



Typical GHB

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Types GHB and HGHB Bolt-On Panelboard Circuit Breakers (15–100 Amperes)

Standards and Certifications

These breakers meet the requirements of Federal Specification W-C-375b as follows:

- Type GHB, 120 and 240 V:
  - Single-pole: Class 11a
  - Two-, three-pole: Classes 10b, 11b, 12b, 14b, 15b
  - UL/CSA
- Type GHB, 277 and 480Y/277V:
  - Single-pole: Classes 12c, 13a
  - Two-, three-pole: Class 13b
  - Type HGHB 277V
  - Type GHQ 277V

Listed

Product Selection

Typical GHB

Type GHB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units ①

Continuous Ampere Rating at 40 °C	277/480 Vac Maximum, 125 Vdc Maximum ② Single-Pole Catalog Number	277/480 Vac Maximum, 125/250 Vdc Maximum Two-Pole Catalog Number	277/480 Vac Maximum, 125/250 Vdc Maximum ③ Three-Pole Catalog Number
15	**GHB1015** ④⑤	**GHB2015** ④	**GHB3015** ④
20	**GHB1020** ④⑤	**GHB2020** ④	**GHB3020** ④
25	**GHB1025**	**GHB2025**	**GHB3025**
30	**GHB1030**	**GHB2030**	**GHB3030**
35	**GHB1035**	**GHB2035**	**GHB3035**
40	**GHB1040**	**GHB2040**	**GHB3040**
45	**GHB1045**	**GHB2045**	**GHB3045**
50	**GHB1050**	**GHB2050**	**GHB3050**
60	**GHB1060**	**GHB2060**	**GHB3060**
70	**GHB1070**	**GHB2070**	**GHB3070**
80	**GHB1080**	**GHB2080**	**GHB3080**
90	**GHB1090**	**GHB2090**	**GHB3090**
100	**GHB1100**	**GHB2100**	**GHB3100**

Type HGHB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	277 Vac Maximum, 125 Vdc Maximum Single-Pole Catalog Number
15	**HGHB1015** ⑥
20	**HGHB1020** ⑥
25	**HGHB1025**
30	**HGHB1030**

Notes

① 480Y/277 V, circuit breakers (Type GHB) not suitable for three-phase delta (480 V).
② Single-pole breakers can be applied in DC systems from 15 through 70 amperes; 80 through 100 amperes devices are not suitable for DC application.
③ Use two outside poles.
④ Uses 0.190 (4.83) –32 screw type clamp terminals.
⑤ Add suffix HID for High Intensity Discharge (HID) applications. 15 and 20 ampere, single-pole are SWD rated.
⑥ 15 and 20 ampere, single-pole are SWD rated.

Dimensions

Approximate Dimensions in Inches (mm)

2

GDB-Frame, Three-Pole

Front View



Side View



Single-Phase (requires two poles)

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Type GHBGFEP Bolt-On Panelboard 30 mA Industrial Ground Fault Circuit Protectors (15–100 Amperes)

Product Description

- 15–60 amperes, 277 V, 50/60 Hz
- Operational voltage 240 V to 305 V

Standards and Certifications

These circuit breakers meet the requirements of UL 489 and UL 1053.

UL Listed

Product Selection

Type GHBGFEP Bolt-On Panelboard 30 mA Industrial Ground Fault Circuit Protectors with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	Single-Phase (Requires Two Poles) 277 Vac, 30 mA Catalog Number
15	**GHBGFEP1015**
20	**GHBGFEP1020**
30	**GHBGFEP1030**
40	**GHBGFEP1040**
50	**GHBGFEP1050**
60	**GHBGFEP1060**

Technical Data and Specifications

Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (Symmetrical Amperes) 277 Vac (50/60 Hz)
GHBGFEP	1	14,000

Dimensions

Approximate Dimensions in Inches (mm)

2

GHB-Frame, Three-Pole

Front View



Side View



Typical GHC

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Types GHC and HGHC Circuit Breakers (15–100 Amperes)

Product Description

- 15–100 amperes
- 120, 240, 277, 480Y/277V, 50/60 Hz, 125, 125/250 Vdc
- Single-, two- and three-pole
- Cable in, cable out
- Does not include mounting hardware

Standards and Certifications

These breakers meet the requirements of Federal Specification W-C-37b as follows:

- Type GHC, 277 and 480Y/277V:
  - Single-pole: Classes 12c, 13a
  - Two-, three-pole: Class 13b
  - UL/CSA

Listed

Product Selection

Type GHC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	277 Vac Maximum, 125 Vdc Maximum ① Single-Pole Catalog Number	480Y/277 Vac Maximum, 125/250 Vdc Maximum Two-Pole Catalog Number	480Y/277 Vac Maximum, 125/250 Vdc Maximum ② Three-Pole Catalog Number
15	**GHC1015** ③④	**GHC2015** ③	**GHC3015** ③
20	**GHC1020** ③④	**GHC2020** ③	**GHC3020** ③
25	**GHC1025**	**GHC2025**	**GHC3025**
30	**GHC1030**	**GHC2030**	**GHC3030**
35	**GHC1035**	**GHC2035**	**GHC3035**
40	**GHC1040**	**GHC2040**	**GHC3040**
45	**GHC1045**	**GHC2045**	**GHC3045**
50	**GHC1050**	**GHC2050**	**GHC3050**
60	**GHC1060**	**GHC2060**	**GHC3060**
70	**GHC1070**	**GHC2070**	**GHC3070**
80	**GHC1080**	**GHC2080**	**GHC3080**
90	**GHC1090**	**GHC2090**	**GHC3090**
100	**GHC1100**	**GHC2100**	**GHC3100**

Type HGHC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	277 Vac Maximum, 125 Vdc Maximum Single-Pole Catalog Number
15	**HGHC1015** ⑤
20	**HGHC1020** ⑤
25	**HGHC1025**
30	**HGHC1030**

Notes

① 15 through 70 ampere circuit breakers only.

② Single-pole breakers can be applied in DC systems from 15 through 70 ampere; 80 through 100 ampere devices are not suitable for DC application.

③ Uses 0.190–32 screw type clamp terminals.

④ Add suffix HID for High Intensity Discharge (HID) applications. 15 and 20 ampere, single-pole are SWD rated.

⑤ 15 and 20 ampere, single-pole are SWD rated.

Single-Phase (requires two-pole spaces)

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Type GHCGFEP Cable-In/Cable-Out 30 mA Industrial Ground Fault Circuit Protectors (15–100 Amperes)

Product Description

- 15–60 amperes, 277 V, 50/60 Hz
- Operational voltage 240–305 V

Standards and Certifications

These circuit breakers meet the requirements of UL 489 and UL 1053.

Listed

Product Selection

Type GHCGFEP 30 mA Industrial Ground Fault Circuit Protectors with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	Single-Phase (Requires Two Poles) 277V, 30 mA Catalog Number
15	**GHCGFEP1015**
20	**GHCGFEP1020**
30	**GHCGFEP1030**
40	**GHCGFEP1040**
50	**GHCGFEP1050**
60	**GHCGFEP1060**

Technical Data and Specifications

Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (Symmetrical Amperes) 277 Vac (50/60 Hz)
GHCGFEP	1	14,000

Special Purpose Circuit Breakers

Contents

Description	Page
Product Overview	V4-T2-116
Standards and Certifications	V4-T2-117
Quick Reference	V4-T2-118
G-Frame (15–100 Amperes)	V4-T2-121
F-Frame (10–225 Amperes)	V4-T2-135
J-Frame (70–250 Amperes)	V4-T2-153
K-Frame (70–400 Amperes)	V4-T2-161
L-Frame (125–600 Amperes)	V4-T2-185
M-Frame (300–800 Amperes)	V4-T2-211
N-Frame (400–1200 Amperes)	V4-T2-222
R-Frame (800–2500 Amperes)	V4-T2-237
Motor Circuit Protectors (MCP)	V4-T2-256
Motor Protection Circuit Breakers (MPCB)	V4-T2-267
Type ELC Current Limiter Attachment (Size 0–4)	V4-T2-269
Current Limiting Circuit Breaker Module	V4-T2-270
Internal Accessories	V4-T2-273
External Accessories	V4-T2-306

Special Purpose GHC Circuit Breakers (15–100 Amperes)

Product Description

Eaton's Type GHC circuit breakers have binding head screw-type terminals on line and load side. These circuit breakers with screw-type terminals (0.190–32) will be marked "Special purpose breaker not for general use." To order this special breaker, use the catalog number from the tables on this page.

Product Selection

Type GHC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Continuous Ampere Rating at 40 °C	277 Vac Maximum, 125 Vdc Maximum ① Single-Pole Catalog Number	480Y/277 Vac Maximum, 125/250 Vdc Maximum Two-Pole Catalog Number	480Y/277 Vac Maximum, 125/250 Vdc Maximum ② Three-Pole Catalog Number
25	**GHC1025D**	**GHC2025D**	**GHC3025D**
30	**GHC1030D**	**GHC2030D**	**GHC3030D**
35	**GHC1035D**	**GHC2035D**	**GHC3035D**
40	**GHC1040D**	**GHC2040D**	**GHC3040D**
45	**GHC1045D**	**GHC2045D**	**GHC3045D**
50	**GHC1050D**	**GHC2050D**	**GHC3050D**
60	**GHC1060D**	**GHC2060D**	**GHC3060D**
70	**GHC1070D**	**GHC2070D**	**GHC3070D**
80	**GHC1080D**	**GHC2080D**	**GHC3080D**
90	**GHC1090D**	**GHC2090D**	**GHC3090D**
100	**GHC1100D**	**GHC2100D**	**GHC3100D**

Type GHB and GHC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units for HID Lighting Applications

Type	Continuous Ampere Rating at 40 °C	277 Vac Maximum Single-Pole Catalog Number
Cable-in	15	**GHC1015HID**
	20	**GHC1020HID**
Bolt-on	15	**GHB1015HID**
	20	**GHB1020HID**

Notes

① Single-pole breakers can be applied in DC systems from 15 through 70 amperes; 80 through 100 amperes devices are not suitable for DC application.

② Use two outside poles.

Typical F-Frame Breaker
F-Frame Breaker with Electronic Trip Unit

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	
Catalog Number Selection	**V4-T2-136**
Product Selection	**V4-T2-138**
Accessories	**V4-T2-149**
Technical Data and Specifications	**V4-T2-150**
Dimensions and Weights	**V4-T2-152**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

F-Frame (10–225 Amperes)

Product Description

- All Eaton's F-Frame circuit breakers are HACR rated
- All circuit breakers 10 through 30 amperes are suitable for HID (high intensity discharge) use
- All F-Frame circuit breakers are suitable for reverse feed use

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

FD-Frame Circuit Breakers with Thermal-Magnetic Trip Unit Technology

FDC 3 100 L

Circuit Breaker Type
EHD
FDB
FD
HFD
FDC

Number of Poles
1 = 1 pole
2 = 2 poles
3 = 3 poles
4 = 4 poles

Trip Amperes
010
015
020
025
030
035
040
045
050
060
070
080
090
100
110
125
150
175 (FD, HFD, FDC, two-, three-, four-pole only)
200 (FD, HFD, FDC, two-, three-, four-pole only)
225 (FD, HFD, FDC, two-, three-, four-pole only)

Suffix
E = 100% protected (four-pole only) neutral pole
EH = 50% protected (four-pole only)
K = High magnetic molded case switch
L = Line and load terminals
S = Stainless steel terminals
V = 50 °C calibration
W = Without terminals
Y = Line terminals only
Z = Aluminum terminals (≤100 amperes)

EDC 3 200 L

Circuit Breaker Type
EDB
EDS
ED
EDH
EDC

Number of Poles
2 = 2 poles
3 = 3 poles

Trip Amperes
100
125
150
175
200
225

Suffix
L = Line and load terminals
W = Without terminals
Y = Line terminals only
Z = Aluminum terminals (100 amperes)

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

FD-Frame Circuit Breakers with 210+ Electronic Trip Unit Technology



FD-Frame Circuit Breakers with 310+ Electronic Trip Unit Technology



Product Selection

Type ED Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units Suitable for Reverse Feed

	240 Vac Maximum, 125 Vdc (Includes Terminals on Load End Only) 65 kAIC at 240 Vac	
	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number
15	ED2015	ED3015
20	ED2020	ED3020
25	ED2025	ED3025
30	ED2030	ED3030
35	ED2035	ED3035
40	ED2040	ED3040
50	ED2050	ED3050
60	ED2060	ED3060
100	ED2100	ED3100
125	ED2125	ED3125
150	ED2150	ED3150
175	ED2175	ED3175
200	ED2200	ED3200
225	ED2225	ED3225

Type EDH Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units Suitable for Reverse Feed

	240 Vac Maximum, 125 Vdc (Includes Terminals on Load End Only) 100 kAIC at 240 Vac	
	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number
15	—	—
20	—	—
25	—	—
30	—	—
35	—	—
40	—	—
50	—	—
60	—	—
100	EDH2100	EDH3100
125	EDH2125	EDH3125
150	EDH2150	EDH3150
175	EDH2175	EDH3175
200	EDH2200	EDH3200
225	EDH2225	EDH3225

Type EDC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units Suitable for Reverse Feed

	240 Vac Maximum, 125 Vdc (Includes Terminals on Load End Only) 200 kAIC at 240 Vac	
	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number
15	—	—
20	—	—
25	—	—
30	—	—
35	—	—
40	—	—
50	—	—
60	—	—
100	**EDC2100**	**EDC3100**
125	**EDC2125**	**EDC3125**
150	**EDC2150**	**EDC3150**
175	**EDC2175**	**EDC3175**
200	**EDC2200**	**EDC3200**
225	**EDC2225**	**EDC3225**

Type EDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units Suitable for Reverse Feed

	240 Vac Maximum, 125 Vdc (Includes Terminals on Load End Only) 22 kAIC at 240 Vac	
	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number
100	**EDB2100**	**EDB3100**
110	**EDB2110**	**EDB3110**
125	**EDB2125**	**EDB3125**
150	**EDB2150**	**EDB3150**
175	**EDB2175**	**EDB3175**
200	**EDB2200**	**EDB3200**
225	**EDB2225**	**EDB3225**

Type EDS Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units Suitable for Reverse Feed

	240 Vac Maximum, 125 Vdc (Includes Terminals on Load End Only) 42 kAIC at 240 Vac	
	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number
100	**EDS2100**	**EDS3100**
110	**EDS2110**	**EDS3110**
125	**EDS2125**	**EDS3125**
150	**EDS2150**	**EDS3150**
175	**EDS2175**	**EDS3175**
200	**EDS2200**	**EDS3200**
225	**EDS2225**	**EDS3225**

Type EHD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (Includes Terminals on Load End Only)

	277 Vac Maximum, 125 Vdc 14 kAIC at 277 Vac	480 Vac Maximum, 250 Vdc 14 kAIC at 480 Vac	
	Single-Pole	Two-Pole	Three-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number
10 ①	**EHD1010**	**EHD2010**	**EHD3010**
15	**EHD1015** ②	**EHD2015**	**EHD3015**
20	**EHD1020** ②	**EHD2020**	**EHD3020**
25	**EHD1025**	**EHD2025**	**EHD3025**
30	**EHD1030**	**EHD2030**	**EHD3030**
35	**EHD1035**	**EHD2035**	**EHD3035**
40	**EHD1040**	**EHD2040**	**EHD3040**
45	**EHD1045**	**EHD2045**	**EHD3045**
50	**EHD1050**	**EHD2050**	**EHD3050**
60	**EHD1060**	**EHD2060**	**EHD3060**
70	**EHD1070**	**EHD2070**	**EHD3070**
80	**EHD1080**	**EHD2080**	**EHD3080**
90	**EHD1090**	**EHD2090**	**EHD3090**
100	**EHD1100**	**EHD2100**	**EHD3100**

Notes

① Not UL listed. 5 kAIC interrupting rating.

② UL listed for SWD applications, see NEC Article 240.83(d).

Type FDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (Includes Terminals on Load End Only)

	600 Vac Maximum, 250 Vdc 14 kAIC at 600 Vac		
	Two-Pole	Three-Pole	Four-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number
10 ①	**FDB2010**	**FDB3010**	**FDB4010**
15	**FDB2015**	**FDB3015**	**FDB4015**
20	**FDB2020**	**FDB3020**	**FDB4020**
25	**FDB2025**	**FDB3025**	**FDB4025**
30	**FDB2030**	**FDB3030**	**FDB4030**
35	**FDB2035**	**FDB3035**	**FDB4035**
40	**FDB2040**	**FDB3040**	**FDB4040**
45	**FDB2045**	**FDB3045**	**FDB4045**
50	**FDB2050**	**FDB3050**	**FDB4050**
60	**FDB2060**	**FDB3060**	**FDB4060**
70	**FDB2070**	**FDB3070**	**FDB4070**
80	**FDB2080**	**FDB3080**	**FDB4080**
90	**FDB2090**	**FDB3090**	**FDB4090**
100	**FDB2100**	**FDB3100**	**FDB4100**
110	**FDB2110**	**FDB3110**	**FDB4110**
125	**FDB2125**	**FDB3125**	**FDB4125**
150	**FDB2150**	**FDB3150**	**FDB4150**

Notes

① Not UL listed. 5 kAIC interrupting rating.

② UL listed for SWD applications, see NEC Article 240.83(d).

Type FD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (Includes Terminals on Load End Only)

	277 Vac Maximum, 125 Vdc 35 kAIC at 277 Vac	600 Vac Maximum, 250 Vdc 35 kAIC at 480 Vac		
	Single-Pole	Two-Pole	Three-Pole	Four-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number	Catalog Number
10 ①	**FD1010**	—	—	—
15	**FD1015** ②	**FD2015**	**FD3015**	**FD4015**
20	**FD1020** ②	**FD2020**	**FD3020**	**FD4020**
25	**FD1025**	**FD2025**	**FD3025**	**FD4025**
30	**FD1030**	**FD2030**	**FD3030**	**FD4030**
35	**FD1035**	**FD2035**	**FD3035**	**FD4035**
40	**FD1040**	**FD2040**	**FD3040**	**FD4040**
45	**FD1045**	**FD2045**	**FD3045**	**FD4045**
50	**FD1050**	**FD2050**	**FD3050**	**FD4050**
60	**FD1060**	**FD2060**	**FD3060**	**FD4060**
70	**FD1070**	**FD2070**	**FD3070**	**FD4070**
80	**FD1080**	**FD2080**	**FD3080**	**FD4080**
90	**FD1090**	**FD2090**	**FD3090**	**FD4090**
100	**FD1100**	**FD2100**	**FD3100**	**FD4100**
110	**FD1110**	**FD2110**	**FD3110**	**FD4110**
125	**FD1125**	**FD2125**	**FD3125**	**FD4125**
150	**FD1150**	**FD2150**	**FD3150**	**FD4150**
175	—	**FD2175**	**FD3175**	**FD4175**
200	—	**FD2200**	**FD3200**	**FD4200**
225	—	**FD2225**	**FD3225**	**FD4225**

Notes

① Not UL listed. 5 kAIC interrupting rating.

② UL listed for SWD applications, see NEC Article 240.83(d).

Type HFD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (Includes Terminals on Load End Only)

	277 Vac Maximum, 125 Vdc 65 kAIC at 277 Vac	600 Vac Maximum, 250 Vdc 65 kAIC at 480 Vac		
	Single-Pole	Two-Pole	Three-Pole	Four-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number	Catalog Number
15	HFD1015 ①	HFD2015	HFD3015	HFD4015
20	HFD1020 ①	HFD2020	HFD3020	HFD4020
25	HFD1025	HFD2025	HFD3025	HFD4025
30	HFD1030	HFD2030	HFD3030	HFD4030
35	HFD1035	HFD2035	HFD3035	HFD4035
40	HFD1040	HFD2040	HFD3040	HFD4040
45	HFD1045	HFD2045	HFD3045	HFD4045
50	HFD1050	HFD2050	HFD3050	HFD4050
60	HFD1060	HFD2060	HFD3060	HFD4060
70	HFD1070	HFD2070	HFD3070	HFD4070
80	HFD1080	HFD2080	HFD3080	HFD4080
90	HFD1090	HFD2090	HFD3090	HFD4090
100	HFD1100	HFD2100	HFD3100	HFD4100
110	HFD1110	HFD2110	HFD3110	HFD4110
125	HFD1125	HFD2125	HFD3125	HFD4125
150	HFD1150	HFD2150	HFD3150	HFD4150
175	—	HFD2175	HFD3175	HFD4175
200	—	HFD2200	HFD3200	HFD4200
225	—	HFD2225	HFD3225	HFD4225

Note

① UL listed for SWD applications, see NEC Article 240.83(d).

Type FDC Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (Includes Terminals on Load End Only)

	600 Vac Maximum, 250 Vdc 100 kAIC at 480 Vac		
	Two-Pole	Three-Pole	Four-Pole
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number
15	**FDC2015**	**FDC3015**	**FDC4015**
20	**FDC2020**	**FDC3020**	**FDC4020**
25	**FDC2025**	**FDC3025**	**FDC4025**
30	**FDC2030**	**FDC3030**	**FDC4030**
35	**FDC2035**	**FDC3035**	**FDC4035**
40	**FDC2040**	**FDC3040**	**FDC4040**
45	**FDC2045**	**FDC3045**	**FDC4045**
50	**FDC2050**	**FDC3050**	**FDC4050**
60	**FDC2060**	**FDC3060**	**FDC4060**
70	**FDC2070**	**FDC3070**	**FDC4070**
80	**FDC2080**	**FDC3080**	**FDC4080**
90	**FDC2090**	**FDC3090**	**FDC4090**
100	**FDC2100**	**FDC3100**	**FDC4100**
110	**FDC2110**	**FDC3110**	**FDC4110**
125	**FDC2125**	**FDC3125**	**FDC4125**
150	**FDC215**	**FDC3150**	**FDC4150**
175	**FDC2175**	**FDC3175**	**FDC4175**
200	**FDC2200**	**FDC3200**	**FDC4200**
225	**FDC2225**	**FDC3225**	**FDC4225**

Types FDE, HFDE and FDCE 310+ Electronic Circuit Breakers with Non-Interchangeable Trip Units

See 310+ adjustability specifications on **Page V4-T2-151**.

	Digitrip RMS 310+ Trip Unit Only				
	Standard	Optional			
	LS	LSI	LSG	LSIG	
Maximum Ampere Rating	Adjustable Short Time Pickup with I^2t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG Catalog Number
35 kAIC at 480 Vac / 18 kAIC at 600 Vac					
80	**FDE308033**	**FDE308032**	**FDE308035**	**FDE308036**	**CTF080**
160	**FDE316033**	**FDE316032**	**FDE316035**	**FDE316036**	**CTF160**
225	**FDE322533**	**FDE322532**	**FDE322535**	**FDE322536**	**CTF225**
65 kAIC at 480 Vac / 25 kAIC at 600 Vac					
80	**HFDE308033**	**HFDE308032**	**HFDE308035**	**HFDE308036**	**CTF080**
160	**HFDE316033**	**HFDE316032**	**HFDE316035**	**HFDE316036**	**CTF160**
225	**HFDE322533**	**HFDE322532**	**HFDE322535**	**HFDE322536**	**CTF225**
100 kAIC at 480 Vac / 25 kAIC at 600 Vac					
80	**FDCE308033**	**FDCE308032**	**FDCE308035**	**FDCE308036**	**CTF080**
160	**FDCE316033**	**FDCE316032**	**FDCE316035**	**FDCE316036**	**CTF160**
225	**FDCE322533**	**FDCE322532**	**FDCE322535**	**FDCE322536**	**CTF225**

Types FDE, HFDE, and FDCE 210+ Electronic Circuit Breakers with Non-Interchangeable Trip Units

	Digitrip RMS 210+ Trip Unit Only	
	Standard	Optional
	LI Adjustable Instantaneous	LSI Adjustable Short Time Pickup and Delay
Maximum Ampere Rating	Catalog Number	Catalog Number
35 kAIC at 480 Vac / 18 kAIC at 600 Vac		
100	**FDE310021**	**FDE310022**
150	**FDE315021**	①
225	**FDE322521**	**FDE322522**
65 kAIC at 480 Vac / 25 kAIC at 600 Vac		
100	**HFDE310021**	**HFDE310022**
150	**HFDE315021**	①
225	**HFDE322521**	**HFDE322522**
100 kAIC at 480 Vac / 25 kAIC at 600 Vac ②		
100	**FDCE310021**	**FDCE310022**
150	**FDCE315021**	①
225	**FDCE322521**	**FDCE322522**

210+ Trip Electronic Trip Units Amperage Settings

Circuit Breaker Type	Frame	Ratings
FDE, HFDE, FDCE	225	100, 110, 125, 150, 175, 200, 225
FDE, HFDE, FDCE	150	70, 80, 90, 100, 110, 125, 150
FDE, HFDE, FDCE	100	40, 50, 60, 70, 80, 90, 100

FDE 310+ Electronic Breaker with Zone Selective Interlocking

Ampere Rating	LSI w/ZSI Catalog Number	LSIG w/ZSI Catalog Number
35 kAIC at 480 Vac / 18 kAIC at 600 Vac		
80	**FDE308032ZG**	**FDE308036ZG**
160	**FDE316032ZG**	**FDE316036ZG**
225	**FDE322532ZG**	**FDE322536ZG**
65 kAIC at 480 Vac / 25 kAIC at 600 Vac		
80	**HFDE308032ZG**	**HFDE308036ZG**
160	**HFDE316032ZG**	**HFDE316036ZG**
225	**HFDE322532ZG**	**HFDE322536ZG**
100 kAIC at 480 Vac / 25 kAIC at 600 Vac		
80	**FDCE308032ZG**	**FDCE308036ZG**
160	**FDCE316032ZG**	**FDCE316036ZG**
225	**FDCE322532ZG**	**FDCE322536ZG**

Digitrip 310+ Electronic Trip Units Amperage Settings

Circuit Breaker Type	Frame	Ratings
FDE, HFDE, FDCE	225	100, 110, 125, 150, 160, 175, 200, 225
FDE, HFDE, FDCE	160	60, 70, 80, 90, 100, 125, 150, 160
FDE, HFDE, FDCE	80	15, 20, 30, 40, 50, 60, 70, 80

Notes

① For 210+ trip unit, 150 A not available with LSI trip unit; entire range is covered by 100 A and 225 A frames.

② Contact the product line for availability.

Molded Case Switches

Eaton's molded case switches are used as compact switches in applications requiring high current switching capabilities. Molded case switches are constructed of circuit breaker components and are of the high instantaneous automatic type. Molded case switches are listed in accordance with Underwriters Laboratories Standard UL 489.

Molded Case Switches

	Complete Circuit Breaker with Load Side Terminals Only		
	480 Vac Maximum, 250 Vdc	600 Vac Maximum, 250 Vdc	
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Catalog Number	Catalog Number
Two-Pole			
100	**EHD2100K**	**FD2100K**	**HFD2100K**
150	—	**FD2150K**	**HFD2150K**
225	—	**FD2225K**	**HFD2225K**
Three-Pole			
100	**EHD3100K**	**FD3100K**	**HFD3100K**
150	—	**FD3150K**	**HFD3150K**
225	—	**FD3225K**	**HFD3225K**
Four-Pole			
100	—	**FD4100K**	**HFD4100K**
150	—	**FD4150K**	**HFD4150K**
225	—	**FD4225K**	**HFD4225K**

Note

Molded case switches will open above 1800 amperes.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

Line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. Except as noted, terminals comply with Underwriters Laboratories Standards UL 486A and UL 486B. Unless otherwise specified, F-Frame circuit breakers are factory equipped with load terminals only.

Ordering Information

F-Frame circuit breakers and molded case switches have load terminals only as standard equipment. When standard line-end terminals (same as standard load-end terminals) are required, add Suffix **L** to the circuit breaker catalog number. When non-standard or optional line and/or load terminals are required, order by style number. Specify if factory installation is required.

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range	Metric Wire Range mm^2	Package of Three Terminals Catalog Number
Standard Pressure Type Terminals					
20 (EHD)	Steel	Cu/Al	14–10	2.5–4	**3T20FB** ②
100	Steel	Cu/Al	14–1/0	2.5–50	**3T100FB**
225	Aluminum	Cu/Al	4–4/0	25–95	**3TA225FD**
Optional Pressure Terminals					
50	Aluminum	Cu/Al	14–4	2.5–25	**3TA50FB** ②
100	Aluminum	Cu/Al	14–1/0	2.5–50	**3TA100FD**
200	Stainless steel	Cu	4–4/0	25–95	**3T150FB**
225	Copper	Cu	4–4/0	25–95	**3T225FD**
225	Aluminum	Cu/Al	6–300 kcmil	16–150	**3TA225FDK3** ③
225	Aluminum	Cu/Al	6–300 kcmil	16–150	**3TA225FDK** ③④

Notes

① Use on FDE, HFDE and FDCE electronic trip only.
② Not for use with ED, EDH, EDC breakers.
③ Includes terminal shield kit. Adds approximately 3 inches (76.2) to breaker height. Available for use on three-pole breaker only.
④ Replacement use only.

Line and Load Terminals



3T20FB

Assemble wire clamp to bottom of conductor as shown.



3T100FB, 3T150FB

Insert collar enclosing conductor as shown. Locate nut on top of conductor and tighten securely with screw and washer.
Caution: Collar must surround conductor.



3TA225FD

Insert collar enclosing conductor and center on extrusion on collar. Install clip with legs on top of conductor and snap end around bottom of collar.



3TA50FB

Assemble collar on top of conductor as shown. Tighten securely with screw and washer.



3TA100FD

Collar slides onto conductor and is held in position by a screw and lockwasher.



3TA225FDK3 (Up to 150 mm^2)

Assemble collar on top of conductor as shown. Tighten securely with screw and washer. Terminal shield must be used with this collar.
Note: For 185 mm^2, use 3TA225FDK1.
Same illustration for 3TA225FDK

Accessories

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

Allowable Accessory Combinations

FD Frame Accessories

Description	Reference Page	Single-Pole	Two-Pole		Three-Pole ①			Four-Pole			
		Center	Left	Right	Left	Center	Right	Left	Center	Right	Neutral
Internal Accessories (Only one internal accessory per pole)											
Alarm lockout switch (make only)	**V4-T2-275**	■									
Alarm lockout (Make/Break)	**V4-T2-275**			■	❑		❑	■			
Alarm lockout (2Make/2Break)	**V4-T2-275**			■	❑		❑	■			
Auxiliary switch (1A, 1B)	**V4-T2-277**			■	■		■	■			■
Auxiliary switch (2A, 2B)	**V4-T2-277**			■	■		■	■			■
Auxiliary switch and alarm switch combination	**V4-T2-279**			■	❑		❑	■			
Shunt trip—standard	**V4-T2-281**			■	■		■	■			■
Shunt trip—low energy	**V4-T2-285**			■	■		■	■			
Undervoltage release mechanism	**V4-T2-287**			■	■		■	■			
External Accessories											
End cap kit	**V4-T2-310**		●	●	●	●	●	●	●	●	●
Keeper nut	**V4-T2-310**	●	●	●	●	●	●	●	●	●	●
Control wire terminal kit	**V4-T2-311**	●	●	●	●	●	●	●	●	●	●
Multiwire connectors	**V4-T2-312**	●	●	●	●	●	●	●	●	●	●
Rear fed terminals	**V4-T2-312**	●	●	●	●	●	●	●	●	●	●
Base mounting hardware	**V4-T2-312**	●	●	●	●	●	●	●	●	●	●
Terminal shields	**V4-T2-314**	●	●	●	●	●	●	●	●	●	●
Terminal end covers	**V4-T2-315**				●	●	●				
Interphase barriers	**V4-T2-315**		●	●	●	●	●	●	●	●	●
Non-padlockable handle block	**V4-T2-316**	■	■			■			■		
Snap-on padlockable handle lock hasp	**V4-T2-316**	■	■			■			■		
Padlockable handle lock hasp	**V4-T2-317**			■	❑		❑	❑		❑	
Cylinder lock	**V4-T2-317**				■						
Key interlock kit	**V4-T2-318**			■	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-319**				●	●	●				
Walking beam interlock—requires two breakers	**V4-T2-319**				●	●	●	●	●	●	●
Electrical (solenoid and motor) operators	**V4-T2-320**				●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-321**		●	●	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-323**	●	●	●	●	●	●	●	●	●	●
Panelboard connecting straps	**V4-T2-324**	●	●	●	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-427**				●	●	●				
LFD current limiter	**V4-T2-326**				●	●	●				
IQ Energy Sentinel	**V4-T2-326**		●	●	●	●	●				
Cause of trip display	**V4-T2-327**				●			●			
Remote mount cause of trip display	**V4-T2-327**				●			●			
Cause of trip LED	**V4-T2-327**				●			●			
Modifications (Refer to Eaton)											
Special calibration	—	●	●	●	●	●	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Note

① Internal accessories are listed with Underwriters Laboratories (UL) for factory installation. They are not listed with UL for field installation.

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600	Volts DC ① 125	250 ②③
EDB	2, 3	22	—	—	—	10	—
EDS	2, 3	42	—	—	—	10	—
ED	2, 3	65	—	—	—	10	—
EDH	2, 3	100	—	—	—	10	—
EDC	2, 3	200	—	—	—	10	—
EHD	1	—	4	—	—	10	—
	2, 3	18	—	14	—	—	10
FDB	2, 3, 4	18	—	14	14	—	10
FD	1	—	35	—	—	10	—
	2, 3, 4	65	—	35	18	—	10
FDE ④	3	65	—	35	18	—	—
HFD	1	—	65	—	—	10	—
	2, 3, 4	100	—	65	25	—	22
HFDE ④	3	100	—	65	25	—	—
FDC ⑤	2, 3, 4	200	—	100	35	—	22
FDCE ④⑤⑥	3	200	—	100	25	—	—

IEC 157-1 (P1) Interrupting Capacity Ratings (P1)

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 220, 240	380, 415	440	500	Volts DC ① 125	250 ②③
EDB	2, 3	22	—	—	—	10	—
EDS	2, 3	42	—	—	—	10	—
ED	2, 3	65	—	—	—	10	—
EDH	2, 3	100	—	—	—	10	—
EDC	2, 3	200	—	—	—	10	—
EHD	1	—	14	—	—	10	—
	2, 3	18	—	14	—	—	10
FDB	2, 3, 4	18	14	14	14	—	10
FD	1	35	—	—	—	10	—
	2, 3, 4	65	35	35	18	—	10
HFD	1	65	—	—	—	10	—
	2, 3, 4	100	65	65	25	—	22
FDC	2, 3, 4	200	100	100	35	—	22

210+ and 310+ Electronic Trip Unit Accessories

Description	210+	310+	Catalog number
Electronic portable test kit	■	■	**MTST230V**
Trip unit tamper protection wire seal	■	■	**5108A03H01**
External neutral sensor (80 A) ⑦		■	**CTF080**
External neutral sensor (160 A) ⑦		■	**CTF160**
External neutral sensor (225 A) ⑦		■	**CTF225**
Compact external neutral sensor (80 A) ⑦		■	**CTFD080**
Compact external neutral sensor (160 A) ⑦		■	**CTFD160**
Compact external neutral sensor (225 A) ⑦		■	**CTFD225**
Breaker-mount cause-of-trip indication		■	**TRIP-LED**
Breaker-mount ammeter module		■	**DIGIVIEW**
Remote-mount ammeter module		■	**DIGIVIEWR06**

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
FDC	240 V/200 kA	41.4	1.41
FDC	480 V/100 kA	38.9	2.50
FDC	600 V/35 kA	29.0	3.00

Notes

① DC ratings apply to substantially non-inductive circuits.
② Two-pole circuit breaker, or two poles of three-pole circuit breaker.
③ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at 22 kA.
④ Electronics available on three-pole only, no DC rating for FDE, HFDE, FDCE.
⑤ Current limiting.
⑥ Check with Eaton for availability.
⑦ Neutral sensor required for four-wire systems if neutral protection is desired; sold separately.

FDE 210+ and 310+ Specifications

Description	Digitrip RMS 210+	Digitrip RMS 310+
Breaker type		
Frame designation	FD	FD
Frames available	100 A, 150 A, 225 A	80 A, 160 A, 225 A
Continuous current range (A)	40–225 A	15–225 A
Ground fault pickup (A)	N/A	16–225 A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100	35, 65, 100
Protection		
Ordering options	LI, LSI	LS, LSI, LSG, LSIG
Arcflash Reduction Maintenance System™ (or Maintenance Mode)	No	No
Interchangeable trip unit	No	No
High load alarm (suffix B20)	No	No
Ground fault alarm with trip (suffix B21)	No	No
Ground fault alarm, no trip (suffix B22)	No	No
Zone selective interlocking (suffix ZG)	No	LSI, LSIG
Cause of trip indication	No	Yes
Thru-cover accessories	No	No
Test kit available	Yes	Yes

FDE 210+ Adjustability Specifications

210+ settings		FD Frame 100 A	150 A	225 A
I_r = continuous current or long delay pickup (amperes) (all 210+)	I_r			
	A	40	70	100
	B	50	80	110
	C	60	90	125
	D	70	100	150
	E	80	110	175
	F	90	125	200
	G (= I_n)	100	150	225
I_i (x I_n)= Instantaneous pickup (210+ LI version)	I_i	100	150	225
	J–2x	200	300	450
	K–2.5x	250	375	565
	L–3x	300	450	675
	M–3.5x	350	525	790
	N–4x	400	600	900
	O–5x	500	750	1125
	P–6x	600	900	1350
	Q–8x	800	1200	1800
	R–10x	1000	1500	2250
	S–12x ①	1200	1800	2400
Fixed instantaneous override (all 210+)		2400	2400	2400
"Isd (x Ir) / tsd = SD profile ② (210+ LSI version)	I_{sd} / t_{sd}	100	150	225
	J	2x / 150	N/A	2x / 150
	K	2x / 300	N/A	2x / 300
	L	2x / I^2t	N/A	2x / I^2t
	M	4x / Inst	N/A	4x / Inst
	N	4x / 150	N/A	4x / 150
	O	4x / I^2t	N/A	4x / I^2t
	P	6x / Inst	N/A	6x / Inst
	Q	6x / 300	N/A	6x / 300
	R	10x / 150	N/A	10x / 150
	S	10x / 300	N/A	10x / 300

FDE 310+ Adjustability Specifications

310+ Settings		FD Frame 80 A	160 A	225 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r			
	A	15	60	100
	B	20	70	110
	C	30	80	125
	D	40	90	150
	E	50	100	160
	F	60	125	175
	G	70	150	200
	H (= I_n)	80	160	225
t_r = long delay time (seconds) (All 310+)	Position 1	2	2	2
	Position 2	4	4	4
	Position 3	7	7	7
	Position 4	10	10	10
	Position 5	12	12	12
	Position 6	15	15	15
	Position 7	20	20	20
	Position 8	24	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x	2x	2x
	Position 2	3x	3x	3x
	Position 3	4x	4x	4x
	Position 4	5x	5x	5x
	Position 5	6x	6x	6x
	Position 6	7x	7x	7x
	Position 7	8x	8x	8x
	Position 8	10x	10x	10x
	Position 9	12x	12x	12x
t_{sd} = short delay time I^2t (milliseconds) (LS, LSG)	Fixed	67 at10x	67 at10x	67 at10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG)	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
I_g = gound fault pickup (amperes) (LSG, LSIG)	Position 1	16	32	45
	Position 2	24	48	67
	Position 3	32	64	90
	Position 4	48	96	135
	Position 5	64	128	180
	Position 6	80	160	225
t_g = ground fault delay time (milliseconds) (LSG, LSIG)	Position 1	Inst	Inst	Inst
	Position 2	120	120	120
	Position 3	300	300	300
Independently Adjustable Instantaneous (I_i) setting	①			
Maintenance Mode pickup (2.5 x I_n) (amperes)	②			

Notes

① Not available for FD. Independently adjustable I_i setting available in LG, NG and RG ALSI and ALSIG trip units.

② Maintenance Mode not available for FD frames. It is available for KD, LD, MDL, LG, NG and RG.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

FD Frame

Number of Poles	Width	Height	Depth
1	1.38 (35.1)	6.00 (152.4)	3.38 (86.0)
2	2.75 (70.0)	6.00 (152.4)	3.38 (86.0)
3	4.13 (105.0)	6.00 (152.4)	3.38 (86.0)
4	5.50 (139.7)	6.00 (152.4)	3.38 (86.0)

FD Frame, Three-Pole

Front View



Side View



Approximate Shipping Weight Lbs (kg)

FD Frame

	Number of Poles			
Breaker Type	1	2	3	4
ED, EDB, EDS, EDH, EDC	—	3 (1.4)	4.5 (2.0)	—
EHD, FDB, FD, HFD, FDC	2 (0.9)	3 (1.4)	4.5 (2.0)	6 (2.7)
FDE, HFDE, FDCE	—	—	4.5 (2.0)	—

Typical J-Frame Breaker

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	
Catalog Number Selection	**V4-T2-154**
Product Selection	**V4-T2-155**
Accessories	**V4-T2-158**
Technical Data and Specifications	**V4-T2-159**
Dimensions and Weights	**V4-T2-160**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

J-Frame (70–250 Amperes)

Product Description

- All Eaton's J-Frame circuit breakers are HACR rated
- J-Frame circuit breakers are available as individual components (frame, trip unit, terminals), or factory assembled complete breakers
- J-Frame circuit breakers with non-interchangeable trip units are suitable for reverse feed use

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

Circuit Breaker/Frame



Trip Unit



Product Selection

Types JD, HJD and JDC Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	Thermal-Magnetic Trip Unit Only ① For Use with Standard or High or Ultra High Interrupting Frames Catalog Number	Standard Terminals Only See Page V4-T2-157 for Optional Terminals Catalog Number
Two-Pole					
70	**JD2070**	**HJD2070**	**JDC2070**	**JT2070T**	**TA250KB** ②
90	**JD2090**	**HJD2090**	**JDC2090**	**JT2090T**	
100	**JD2100**	**HJD2100**	**JDC2100**	**JT2100T**	
125	**JD2125**	**HJD2125**	**JDC2125**	**JT2125T**	
150	**JD2150**	**HJD2150**	**JDC2150**	**JT2150T**	
175	**JD2175**	**HJD2175**	**JDC2175**	**JT2175T**	
200	**JD2200**	**HJD2200**	**JDC2200**	**JT2200T**	
225	**JD2225**	**HJD2225**	**JDC2225**	**JT2225T**	
250	**JD2250**	**HJD2250**	**JDC2250**	**JT2250T**	
Three-Pole					
70	**JD3070**	**HJD3070**	**JDC3070**	**JT3070T**	**TA250KB** ②
90	**JD3090**	**HJD3090**	**JDC3090**	**JT3090T**	
100	**JD3100**	**HJD3100**	**JDC3100**	**JT3100T**	
125	**JD3125**	**HJD3125**	**JDC3125**	**JT3125T**	
150	**JD3150**	**HJD3150**	**JDC3150**	**JT3150T**	
175	**JD3175**	**HJD3175**	**JDC3175**	**JT3175T**	
200	**JD3200**	**HJD3200**	**JDC3200**	**JT3200T**	
225	**JD3225**	**HJD3225**	**JDC3225**	**JT3225T**	
250	**JD3250**	**HJD3250**	**JDC3250**	**JT3250T**	
Four-Pole ③④					
125	**JD4125**	**HJD4125**	**JDC4125**	**JT3125T**	**TA250KB** ②
150	**JD4150**	**HJD4150**	**JDC4150**	**JT3150T**	
175	**JD4175**	**HJD4175**	**JDC4175**	**JT3175T**	
200	**JD4200**	**HJD4200**	**JDC4200**	**JT3200T**	
225	**JD4225**	**HJD4225**	**JDC4225**	**JT3225T**	
250	**JD4250**	**HJD4250**	**JDC4250**	**JT3250T**	

Notes

① Magnetic trip adjustable 5–10 times continuous ampere rating.
② Individually packed.
③ Fully rated neutral pole with no protection.
④ Neutral is in right pole.

Types JD, HJD and JDC Thermal-Magnetic Circuit Breakers—Frame Only

Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac
Catalog Number	Catalog Number	Catalog Number
Two-Pole		
JD2250F	HJD2250F	JDC2250F
Three-Pole		
JD3250F	HJD3250F	JDC3250F
Four-Pole		
JD4250F	HJD4250F	JDC4250F

Type JDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Thermal-Magnetic Trip Units Suitable for Reverse Feed Application

	600 Vac Rated, 250 Vdc Complete Circuit Breaker	
Maximum Continuous Ampere Rating at 40 °C	Without Line and Load Terminals Catalog Number	With Standard Line and Load Terminals Only Catalog Number
Two-Pole		
70	JDB2070W	JDB2070
90	JDB2090W	JDB2090
100	JDB2100W	JDB2100
125	JDB2125W	JDB2125
150	JDB2150W	JDB2150
175	JDB2175W	JDB2175
200	JDB2200W	JDB2200
225	JDB2225W	JDB2225
250	JDB2250W	JDB2250
Three-Pole		
70	JDB3070W	JDB3070
90	JDB3090W	JDB3090
100	JDB3100W	JDB3100
125	JDB3125W	JDB3125
150	JDB3150W	JDB3150
175	JDB3175W	JDB3175
200	JDB3200W	JDB3200
225	JDB3225W	JDB3225
250	JDB3250W	JDB3250

Molded Case Switches

Eaton's molded case switches are used as compact switches in applications requiring high current switching capabilities. Molded case switches are constructed of circuit breaker components and are of the high instantaneous automatic type. Molded case switches are listed in accordance with Underwriters Laboratories Standard UL 489.

Molded Case Switches

	600 Vac Maximum, 250 Vdc Complete Circuit Breaker Only Without Line and Load Terminals		Standard Terminals Only
Maximum Continuous Ampere Rating at 40 °C	Catalog Number	Suitable for Reverse Feed Use Catalog Number	See PageV4-T2-157 for Optional Terminals Catalog Number
Two-Pole			
250	JD2250KW	JDB2250KW	TA250KB ①
	HJD2250KW	HJDB2250KW	—
Three-Pole			
250	JD3250KW	JDB3250KW	TA250KB ①
	HJD3250KW	HJDB3250KW	—
Four-Pole			
250	JD4250KW	JDB4250KW	TA250KB ①
	HJD4250KW	HJDB4250KW	—

Notes

① Individually packed.

Molded case switches may open above 2500 amperes.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

Eaton's line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. All terminals comply with Underwriters Laboratories Standards UL 486A and UL 486B and CSA Standard C22.2 No. 65, or Electrical Bulletin 1165.

Unless otherwise specified, J-Frame circuit breaker line and load terminals are shipped separately for field installation.

The bottom of the standard TA250KB terminal contains a recess that is positioned over the J-Frame circuit breaker terminal conductor.

Ordering Information

J-Frame circuit breakers use Cu/Al terminals as standard. When optional copper-only terminals are required, order by catalog number. Specify if factory installation is required.



T250KB Terminal



TA250KB Terminal (Standard)

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/ No. Conductors	Metric Wire Range mm^2	Catalog Number
Standard Cu/Al Pressure Terminals					
250	Aluminum	Cu/Al	4–350 kcmil	25–185	**TA250KB**
Optional Cu Pressure Terminals					
250	Stainless Steel	Cu	4–350 kcmil	25–185	**T250KB**

Accessories

2

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

JD Frame Accessories

Description	Reference Page	Two-, Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neutral
Internal Accessories (Only One Internal Accessory Per Pole)								
Alarm lockout (Make/Break)	**V4-T2-275**	❑		❑	❑		❑	
Auxiliary switch (1A, 1B)	**V4-T2-277**	■		■	■		■	
Auxiliary switch (2A, 2B)	**V4-T2-277**	■		■	■		■	
Auxiliary switch and alarm switch combination	**V4-T2-279**	❑		❑	❑		❑	
Shunt trip—standard	**V4-T2-282**	■		■	■		■	
Shunt trip—low energy	**V4-T2-285**	■		■	■		■	
Undervoltage release mechanism	**V4-T2-289**	■		■	■		■	
External Accessories								
End cap kit	**V4-T2-310**	●	●	●	●	●	●	●
Plug nut	**V4-T2-311**	●	●	●	●	●	●	●
Control wire terminal kit	**V4-T2-311**	●	●	●	●	●	●	●
Multiwire connectors	**V4-T2-312**	●	●	●	●	●	●	●
Base mounting hardware	**V4-T2-313**	●	●	●	●	●	●	●
Terminal shields	**V4-T2-314**	●	●	●	●	●	●	●
Interphase barriers	**V4-T2-315**	●	●	●	●	●	●	●
Non-padlockable handle block	**V4-T2-316**		■			■		
Padlockable handle block	**V4-T2-316**		■			■		
Padlockable handle lock hasp	**V4-T2-317**	❑		❑	❑		❑	
Cylinder lock	**V4-T2-317**	❑		❑				
Key interlock kit	**V4-T2-318**	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-319**	●	●	●				
Electrical (solenoid) operator	**V4-T2-321**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-321**	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-323**	●	●	●	●	●	●	●
Panelboard connecting straps	**V4-T2-324**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-427**	●	●	●	●	●	●	●
Handle extension	**V4-T2-442**	●	●	●	●	●	●	●
IQ Energy Sentinel	**V4-T2-326**	●	●	●				
Modifications (Refer to Eaton)								
Special calibration	—	●	●	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position

❑ May be mounted on left or right pole—not both

● Accessory available/modification available

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	480	600	Volts DC 125	250 ①②
JDB	2, 3	65	35	18	—	10
JD	2, 3, 4	65	35	18	—	10
HJD	2, 3, 4	100	65	25	—	22
JDC ③	2, 3, 4	200	100	35	—	22

IEC 157-1 (P1) Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	380	415	600	Volts DC 125	250 ①②
JD	2, 3, 4	65	35	35	—	—	10
HJD	2, 3, 4	100	65	65	—	—	22
JDC	2, 3, 4	200	100	100	—	—	22

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
JDC	240 V/200 kA	42.6	1.36
JDC	480 V/100 kA	40.0	3.00
JDC	600 V/35 kA	31.9	3.10

Notes

① Two-pole circuit breaker or two outside poles of three-pole circuit breaker.
② Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at 22 kA.
③ Current limiting.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

JD Frame

Number of Poles	Width	Height	Depth
2, 3	4.13 (105.0)	10.00 (254.0)	4.06 (104.1)
4	5.50 (139.7)	10.00 (254.0)	4.06 (104.1)

JD-Frame, Three-Pole

Front View

Front View Cutout





Side View



Approximate Shipping Weight in Lbs (kg)

JD Frame

Breaker Type	Complete Breaker			Frame Only			Trip Unit		
	Two-Pole	Three-Pole	Four-Pole	Two-Pole	Three-Pole	Four-Pole	Two-Pole	Three-Pole	Four-Pole
JDB	11.25 (5.1)	12.50 (5.7)	—	—	—	—	—	—	—
JD	11.25 (5.1)	12.50 (5.7)	13.25 (6.0)	9.00 (4.1)	10.00 (4.5)	10.50 (4.8)	2.00 (0.9)	2.00 (0.9)	2.25 (1.0)
HJD	11.25 (5.1)	12.50 (5.7)	13.25 (6.0)	9.00 (4.1)	10.00 (4.5)	10.50 (4.8)	2.00 (0.9)	2.00 (0.9)	2.25 (1.0)
JDC	12.25 (5.6)	13.50 (6.1)	14.25 (6.5)	10.00 (4.5)	11.00 (5.0)	11.50 (5.2)	2.00 (0.9)	2.00 (0.9)	2.25 (1.0)

Typical K-Frame Circuit Breaker

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	
Catalog Number Selection	**V4-T2-162**
Product Selection	**V4-T2-164**
Accessories	**V4-T2-180**
Technical Data and Specifications	**V4-T2-181**
Dimensions and Weights	**V4-T2-184**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

K-Frame (70–400 Amperes)

Product Description

- All Eaton K-Frame circuit breakers are HACR rated
- K-Frame circuit breakers are available as individual components (frame, trip unit, terminals), or factory assembled complete breakers
- K-Frame circuit breakers with non-interchangeable trip units are suitable for reverse feed use

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

2

K-Frame with Thermal-Magnetic Trip Unit Technology

Thermal-Magnetic Breakers and Frames ①

KD 3 400 F

Circuit Breaker/ Frame Type
DK
KD
KDB
HKD
KDC

Number of Poles
2 = Two-pole
3 = Three-pole
4 = Four-pole

Circuit Breaker/ Frame Ampere Rating
100
125
150
175
200
225
250
300
350
400

Suffix	
C	= Copper terminals
E	= 50% protected neutral pole (four-pole electronic trip unit circuit breaker only)
F	= Frame only (400 A only)
K	= High-magnetic molded-case switch
V	= 50 ° calibration (thermal-magnetic trip units only)
W	= Without terminals
X	= Load terminals only
Y	= Line side terminals only
Blank	= Standard load and line side terminals

Thermal-Magnetic Trip Unit ①

KT 3 400 F

Trip Unit Type
KT = Thermal-magnetic

Number of Poles
2 = Two-pole
3 = Three-pole
4 = Four-pole

Circuit Breaker/ Frame Ampere Rating
100
125
150
175
200
225
250
300
350
400

Suffix
T = Trip unit only

Notes

① Frames are the same for thermal-magnetic or 310+ electronic trip units, e.g., **KD3400F** or **HKD3400F**. Ampere rating available with electronic trip unit only.

K-Frame with 310+ Electronic Trip Unit Technology ①

310+ Circuit Breakers ②

KDB 3 400 F T36 ZG W

Performance at 480 Vac
KDB = 35 kAIC
HKDB = 65 kAIC
CKDB = 35 kAIC 100% rated
CHKDB = 65 kAIC 100% rated

Number of Poles
3 = Three-pole

Ampere Rating
125
250
400

Frame Designation
F

Trip Unit
T33 = 310+ Electronic LS
T32 = 310+ Electronic LSI
T35 = 310+ Electronic LSG
T36 = 310+ Electronic LSIG
T38 = 310+ Electronic ALSI with Maintenance Mode
T39 = 310+ Electronic ALSIG with Maintenance Mode

Feature
Blank = No feature
B20 = High load alarm
B21 = Ground fault alarm, with trip
B22 = Ground fault alarm, no trip
ZG = Zone selective interlocking

Terminals
W = No terminals
L = Line and load

310+ Electronic Trip Units ③

KES 3 400 LSIG ZG

Trip Unit Type
KES

Number of Poles
3 = Three-pole
4 = Four-pole

Ampere Rating
125
250
400

Trip Unit	
LS	= 310+ Electronic LS
LSI	= 310+ Electronic LSI
LSG	= 310+ Electronic LSG ②
LSIG	= 310+ Electronic LSIG ②
ALSI	= 310+ Electronic LSI with Maintenance Mode
ALSIG	= 310+ Electronic LSIG with Maintenance Mode ②

Feature
Blank = No feature
B20 = High load alarm
B21 = Ground fault alarm, with trip ②
B22 = Ground fault alarm, no trip ②
ZG = Zone selective interlocking

K-Frame with OPTIM Trip Unit Technology

OPTIM Circuit Breakers

KD 3 125 T5 7 W

Circuit Breaker/ Frame Type
KD
HKD
KDC
CKD
CHKD

Number of Poles
3 = Three-pole

Circuit Breaker/Frame Ampere Rating
125
250
400

Trip Model
T5 = Model 550
T10 = Model 1050

Trip Type
2 = LSI
6 = LSIG
7 = LSIA

Suffix
W = Without terminals

Notes

① Cannot combine 'B2X' suffixes with 'B2X' suffixes.

② Not available in four-pole configurations.

③ Frames are the same for thermal-magnetic or 310+ electronic trip units, e.g., **KD3400F**, **HKD3400F**, etc.

Product Selection

Types KD, HKD and KDC Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals ① Catalog Number	Thermal-Magnetic Trip Unit Only ① For Use with Standard or High or Ultra High Interrupting Frames Catalog Number	Standard Terminals Only See Page V4-T2-179 for Optional Terminals Catalog Number
Two-Pole					
100	**KD2100**	**HKD2100**	**KDC2100**	**KT2100T**	**TA300K** ②
125	**KD2125**	**HKD2125**	**KDC2125**	**KT2125T**	**TA300K** ②
150	**KD2150**	**HKD2150**	**KDC2150**	**KT2150T**	**TA300K** ②
175	**KD2175**	**HKD2175**	**KDC2175**	**KT2175T**	**TA300K** ②
200	**KD2200**	**HKD2200**	**KDC2200**	**KT2200T**	**TA300K** ②
225	**KD2225**	**HKD2225**	**KDC2225**	**KT2225T**	**TA300K** ②
250	**KD2250**	**HKD2250**	**KDC2250**	**KT2250T**	**TA350K** ②
300	**KD2300**	**HKD2300**	**KDC2300**	**KT2300T**	**TA350K** ②
350	**KD2350**	**HKD2350**	**KDC2350**	**KT2350T**	**TA350K** ②
400	**KD2400**	**HKD2400**	**KDC2400**	**KT2400T**	**2TA400K** ③
Three-Pole					
100	**KD3100**	**HKD3100**	**KDC3100**	**KT3100T**	**TA300K** ②
125	**KD3125**	**HKD3125**	**KDC3125**	**KT3125T**	**TA300K** ②
150	**KD3150**	**HKD3150**	**KDC3150**	**KT3150T**	**TA300K** ②
175	**KD3175**	**HKD3175**	**KDC3175**	**KT3175T**	**TA300K** ②
200	**KD3200**	**HKD3200**	**KDC3200**	**KT3200T**	**TA300K** ②
225	**KD3225**	**HKD3225**	**KDC3225**	**KT3225T**	**TA300K** ②
250	**KD3250**	**HKD3250**	**KDC3250**	**KT3250T**	**TA350K** ②
300	**KD3300**	**HKD3300**	**KDC3300**	**KT3300T**	**TA350K** ②
350	**KD3350**	**HKD3350**	**KDC3350**	**KT3350T**	**TA350K** ②
400	**KD3400**	**HKD3400**	**KDC3400**	**KT3400T**	**3TA400K** ③
Four-Pole					
100	**KD4100**	**HKD4100**	**KDC4100**	**KT3100T**	**TA300K** ②
125	**KD4125**	**HKD4125**	**KDC4125**	**KT3125T**	**TA300K** ②
175	**KD4175**	**HKD4175**	**KDC4175**	**KT3175T**	**TA300K** ②
200	**KD4200**	**HKD4200**	**KDC4200**	**KT3200T**	**TA300K** ②
225	**KD4225**	**HKD4225**	**KDC4225**	**KT3225T**	**TA300K** ②
250	**KD4250**	**HKD4250**	**KDC4250**	**KT3250T**	**TA350K** ②
300	**KD4300**	**HKD4300**	**KDC4300**	**KT3300T**	**TA350K** ②
350	**KD4350**	**HKD4350**	**KDC4350**	**KT3350T**	**TA350K** ②
400	**KD4400**	**HKD4400**	**KDC4400**	**KT3400T**	**4TA400K** ③

Notes

① Magnetic trip adjustable 5–10 times continuous ampere rating.
② Individually packed.
③ 2TA400K, 3TA400K and 4TA400K terminal kits contain one terminal for each pole and one terminal cover.

Types KD, HKD and KDC Thermal-Magnetic Circuit Breakers—Frame Only

Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Catalog Number	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac Catalog Number
Two-Pole		
KD2400F	HKD2400F	KDC2400F
Three-Pole		
KD3400F	HKD3400F	KDC3400F
Four-Pole		
KD4400F	HKD4400F	KDC4400F

Types KD, HKD and KDC Electronic Circuit Breakers with Interchangeable 310+ Trip Units

Order as individual components: breaker frame, trip unit and terminals. See 310+ adjustability specifications on **Page V4-T2-182**.

Types KD, HKD and KDC Electronic Circuit Breakers with Interchangeable 310+ Trip Units—Three-Pole

	Circuit Breaker Frame Only			Digitrip RMS 310+ Trip Unit Only ①					
				Standard	Options				
			Ultra High Interrupting	LS	LSI	LSG	LSIG		
Max. Cont. Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Delay and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
125	KD3400F	HKD3400F	KDC3400F	KES3125LS	KES3125LSI	KES3125LSG	KES3125LSIG	LGFCT125	See **Page V4-T2-179**
250	KD3400F	HKD3400F	KDC3400F	KES3250LS	KES3250LSI	KES3250LSG	KES3250LSIG	LGFCT250	
400	KD3400F	HKD3400F	KDC3400F	KES3400LS	KES3400LSI	KES3400LSG	KES3400LSIG	LGFCT400	

Types KD, HKD and KDC Electronic Circuit Breakers with Interchangeable 310+ Trip Units—Four-Pole ④⑤

	Circuit Breaker Frame Only			Digitrip RMS 310+ Trip Unit Only ①					
				Standard	Options				
			Ultra High Interrupting	LS	LSI	LSG	LSIG		
Max. Cont. Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Delay and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
125	KD4400F	HKD4400F	KDC4400F	KES4125LS	KES4125LSI	—	—	—	See **Page V4-T2-179**
250	KD4400F	HKD4400F	KDC4400F	KES4250LS	KES4250LSI	—	—	—	
400	KD4400F	HKD4400F	KDC4400F	KES4400LS	KES4400LSI	—	—	—	

Notes

① For AC use only.
② Required for four-wire systems if neutral protection is desired.
③ Included with LSG and LSIG trip units.
④ Trip unit includes protected neutral pole. Use corresponding three-pole trip unit if protected neutral pole is not required.
⑤ Fully rated neutral pole protection is standard. For 50% rated protection on neutral pole, add Suffix **E** to four-pole trip unit catalog number.

2

Type KDB with Digitrip 310+ Non-Interchangeable Trip Unit Suitable for Reverse Feed

See 310+ adjustability specifications on **Page V4-T2-182**.

		Factory Assembled Circuit Breaker Consisting of Frame and Trip Unit Less Terminals ①					
		Standard LS	Optional LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Number of Poles	Adjustable Short Time Pickup with I^2t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
125	3	KDB3125FT33W	KDB3125FT32W	KDB3125FT35W	KDB3125FT36W	LGFCT125	See **Page V4-T2-180**
250	3	KDB3250FT33W	KDB3250FT32W	KDB3250FT35W	KDB3250FT36W	LGFCT250	
400	3	KDB3400FT33W	KDB3400FT32W	KDB3400FT35W	KDB3400FT36W	LGFCT400	

Type HKDB with Digitrip 310+ Non-Interchangeable Trip Unit Suitable for Reverse Feed

See 310+ adjustability specifications on **Page V4-T2-182**.

		Factory Assembled Circuit Breaker Consisting of Frame and Trip Unit Less Terminals ①					
		Standard LS	Optional LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Number of Poles	Adjustable Short Time Pickup with I^2t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
125	3	HKDB3125FT33W	HKDB3125FT32W	HKDB3125FT35W	HKDB3125FT36W	LGFCT125	See **Page V4-T2-180**
250	3	HKDB3250FT33W	HKDB3250FT32W	HKDB3250FT35W	HKDB3250FT36W	LGFCT250	
400	3	HKDB3400FT33W	HKDB3400FT32W	HKDB3400FT35W	HKDB3400FT36W	LGFCT400	

100% Rated Types CKD and CHKD Electronic Circuit Breakers

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at the 75 °C ampacity. All 100% rated circuit breakers have electronic trip units.

100% Rated Types CKD and CHKD Electronic Circuit Breakers—Three-Pole

See 310+ adjustability specifications on **Page V4-T2-182**.

	Circuit Breaker Frame Only		Digitrip RMS 310+ Trip Unit Only					
			Standard	Options				
Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 65 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Delay and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
125	CKD3400F	CHKD3400F	KES3125LS	KES3125LSI	KES3125LSG	KES3125LSIG	LGFCT125	See **Page V4-T2-179**
250	CKD3400F	CHKD3400F	KES3250LS	KES3250LSI	KES3250LSG	KES3250LSIG	LGFCT250	
400	CKD3400F	CHKD3400F	KES3400LS	KES3400LSI	KES3400LSG	KES3400LSIG	LGFCT400	

Notes

① For AC use only.

② Required for four-wire systems if neutral protection is desired.

③ Included with LSG and LSIG trip units.

Types DK and KDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Suitable for reverse feed application.

Types DK and KDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C	240 Vac Rated, 250 Vdc Complete Circuit Breaker			600 Vac Rated, 250 Vdc Complete Circuit Breaker	
	Without Line and Load Terminals	With Line Terminals Only	With Standard Line and Load Terminals Only	Without Line and Load Terminals	With Standard Line and Load Terminals
	Catalog Number	Catalog Number	Catalog Number	Catalog Number	Catalog Number
Two-Pole					
100	—	—	—	**KDB2100W**	**KDB2100**
125	—	—	—	**KDB2125W**	**KDB2125**
150	—	—	—	**KDB2150W**	**KDB2150**
175	—	—	—	**KDB2175W**	**KDB2175**
200	—	—	—	**KDB2200W**	**KDB2200**
225	—	—	—	**KDB2225W**	**KDB2225**
250	**DK2250W**	**DK2250Y**	**DK2250**	**KDB2250W**	**KDB2250**
300	**DK2300W**	**DK2300Y**	**DK2300**	**KDB2300W**	**KDB2300**
350	**DK2350W**	**DK2350Y**	**DK2350**	**KDB2350W**	**KDB2350**
400	**DK2400W**	**DK2400Y**	**DK2400**	**KDB2400W**	**KDB2400**
Three-Pole					
100	—	—	—	**KDB3100W**	**KDB3100**
125	—	—	—	**KDB3125W**	**KDB3125**
150	—	—	—	**KDB3150W**	**KDB3150**
175	—	—	—	**KDB3175W**	**KDB3175**
200	—	—	—	**KDB3200W**	**KDB3200**
225	—	—	—	**KDB3225W**	**KDB3225**
250	**DK3250W**	**DK3250Y**	**DK3250**	**KDB3250W**	**KDB3250**
300	**DK3300W**	**DK3300Y**	**DK3300**	**KDB3300W**	**KDB3300**
350	**DK3350W**	**DK3350Y**	**DK3350**	**KDB3350W**	**KDB3350**
400	**DK3400W**	**DK3400Y**	**DK3400**	**KDB3400W**	**KDB3400**

Molded Case Switches

Eaton's molded case switches are used as compact switches in applications requiring high current switching capabilities. Molded case switches are constructed of circuit breaker components and are of the high instantaneous automatic type. Molded case switches are listed in accordance with Underwriters Laboratories Standard UL 489.

Molded Case Switches

Maximum Continuous Ampere Rating at 40 °C	240 Vac Maximum, 250 Vdc Complete Circuit Breaker with Standard Line and Load Terminals Catalog Number	600 Vac Maximum, 250 Vdc Complete Circuit Breaker with Standard Line and Load Terminals Catalog Number	600 Vac Maximum, 250 Vdc Complete Circuit Breaker with Standard Line and Load Terminals. Suitable for Reverse Feed Use Catalog Number
Two-Pole			
400	**DK2400K**	**KD2400K**	**KDB2400K**
	—	**HKD2400K**	**HKDB2400K**
Three-Pole			
400	**DK3400K**	**KD3400K**	**KDB3400K**
	—	**HKD3400K**	**HKDB3400K**
Four-Pole			
400	—	**KD4400K**	**KDB4400K**
	—	**HKD4400K**	**HKDB4400K**

Note

Molded case switches may open above 4000 amperes.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				
	LSI	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac					
125	**KD3125T52W**	**KD3125T56W**	**KD3125T57W**	70	**ORPK125A70**
				90	**ORPK125A90**
				100	**ORPK125A100**
				110	**ORPK125A110**
				125	**ORPK125A125**
250	**KD3250T52W**	**KD3250T56W**	**KD3250T57W**	125	**ORPK025A125**
				150	**ORPK025A150**
				175	**ORPK025A175**
				200	**ORPK025A200**
				225	**ORPK025A225**
				250	**ORPK025A250**
400	**KD3400T52W**	**KD3400T56W**	**KD3400T57W**	200	**ORPK40A200**
				225	**ORPK40A225**
				250	**ORPK40A250**
				300	**ORPK40A300**
				350	**ORPK40A350**
				400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
125	**HKD3125T52W**	**HKD3125T56W**	**HKD3125T57W**	70	**ORPK125A70**
				90	**ORPK125A90**
				100	**ORPK125A100**
				110	**ORPK125A110**
				125	**ORPK125A125**
250	**HKD3250T52W**	**HKD3250T56W**	**HKD3250T57W**	125	**ORPK025A125**
				150	**ORPK025A150**
				175	**ORPK025A175**
				200	**ORPK025A200**
				225	**ORPK025A225**
				250	**ORPK025A250**
400	**HKD3400T52W**	**HKD3400T56W**	**HKD3400T57W**	200	**ORPK40A200**
				225	**ORPK40A225**
				250	**ORPK40A250**
				300	**ORPK40A300**
				350	**ORPK40A350**
				400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response) OPTIM 550 ②			Digitrip OPTIM Rating Plug Only	
	LSI	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac					
125	**KDC3125T52W**	**KDC3125T56W**	**KDC3125T57W**	70	**ORPK125A70**
				90	**ORPK125A90**
				100	**ORPK125A100**
				110	**ORPK125A110**
				125	**ORPK125A125**
250	**KDC3250T52W**	**KDC3250T56W**	**KDC3250T57W**	125	**ORPK025A125**
				150	**ORPK025A150**
				175	**ORPK025A175**
				200	**ORPK025A200**
				225	**ORPK025A225**
				250	**ORPK025A250**
400	**KDC3400T52W**	**KDC3400T56W**	**KDC3400T57W**	200	**ORPK40A200**
				225	**ORPK40A225**
				250	**ORPK40A250**
				300	**ORPK40A300**
				350	**ORPK40A350**
				400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②			
	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac				
125	**KD3125T106W**	**KD3125T107W**	70	**ORPK125A70**
			90	**ORPK125A90**
			100	**ORPK125A100**
			110	**ORPK125A110**
			125	**ORPK125A125**
250	**KD3250T106W**	**KD3250T107W**	125	**ORPK025A125**
			150	**ORPK025A150**
			175	**ORPK025A175**
			200	**ORPK025A200**
			225	**ORPK025A225**
			250	**ORPK025A250**
400	**KD3400T106W**	**KD3400T107W**	200	**ORPK40A200**
			225	**ORPK40A22**
			250	**ORPK40A250**
			300	**ORPK40A300**
			350	**ORPK40A350**
			400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Factory sealed.

Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ② LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
125	**HKD3125T106W**	**HKD3125T107W**	70	**ORPK125A70**
			90	**ORPK125A90**
			100	**ORPK125A100**
			110	**ORPK125A110**
			125	**ORPK125A125**
250	**HKD3250T106W**	**HKD3250T107W**	125	**ORPK025A125**
			150	**ORPK025A150**
			175	**ORPK025A175**
			200	**ORPK025A200**
			225	**ORPK025A225**
			250	**ORPK025A250**
400	**HKD3400T106W**	**HKD3400T107W**	200	**ORPK40A200**
			225	**ORPK40A225**
			250	**ORPK40A250**
			300	**ORPK40A300**
			350	**ORPK40A350**
			400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Factory sealed.

Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ② LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac				
125	**KDC3125T106W**	**KDC3125T107W**	70	**ORPK125A70**
			90	**ORPK125A90**
			100	**ORPK125A100**
			110	**ORPK125A110**
			125	**ORPK125A125**
250	**KDC3250T106W**	**KDC3250T107W**	125	**ORPK025A125**
			150	**ORPK025A150**
			175	**ORPK025A175**
			200	**ORPK025A200**
			225	**ORPK025A225**
			250	**ORPK025A250**
400	**KDC3400T106W**	**KDC3400T107W**	200	**ORPK40A200**
			225	**ORPK40A225**
			250	**ORPK40A250**
			300	**ORPK40A300**
			350	**ORPK40A350**
			400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Factory sealed.

100% Rated Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

100% Rated Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				Fixed Rating Plug
	LSI	LSIG	LSIA		
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac					
125	**CKD3125T52W**	**CKD3125T56W**	**CKD3125T57W**	70	**ORPK125A70**
				90	**ORPK125A90**
				100	**ORPK125A100**
				110	**ORPK125A110**
				125	**ORPK125A125**
250	**CKD3250T52W**	**CKD3250T56W**	**CKD3250T57W**	125	**ORPK025A125**
				150	**ORPK025A150**
				175	**ORPK025A175**
				200	**ORPK025A200**
				225	**ORPK025A225**
				250	**ORPK025A250**
400	**CKD3400T52W**	**CKD3400T56W**	**CKD3400T57W**	200	**ORPK40A200**
				225	**ORPK40A225**
				250	**ORPK40A250**
				300	**ORPK40A300**
				350	**ORPK40A350**
				400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number (refer to **Page V4-T2-293**).

100% Rated Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				
	LSI	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
125	**CHKD3125T52W**	**CHKD3125T56W**	**CHKD3125T57W**	70	**ORPK125A70**
				90	**ORPK125A90**
				100	**ORPK125A100**
				110	**ORPK125A110**
				125	**ORPK125A125**
250	**CHKD3250T52W**	**CHKD3250T56W**	**CHKD3250T57W**	125	**ORPK025A125**
				150	**ORPK025A150**
				175	**ORPK025A175**
				200	**ORPK025A200**
				225	**ORPK025A225**
				250	**ORPK025A250**
400	**CHKD3400T52W**	**CHKD3400T56W**	**CHKD3400T57W**	200	**ORPK40A200**
				225	**ORPK40A225**
				250	**ORPK40A250**
				300	**ORPK40A300**
				350	**ORPK40A350**
				400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

100% Rated Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

100% Rated Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②			
	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac				
125	**CKD3125T106W**	**CKD3125T107W**	70	**ORPK125A70**
			90	**ORPK125A90**
			100	**ORPK125A100**
			110	**ORPK125A110**
			125	**ORPK125A125**
250	**CKD3250T106W**	**CKD3250T107W**	125	**ORPK025A125**
			150	**ORPK025A150**
			175	**ORPK025A175**
			200	**ORPK025A200**
			225	**ORPK025A225**
			250	**ORPK025A250**
400	**CKD3400T106W**	**CKD3400T107W**	200	**ORPK40A200**
			225	**ORPK40A225**
			250	**ORPK40A250**
			300	**ORPK40A300**
			350	**ORPK40A350**
			400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Factory sealed.

100% Rated Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②			
	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
125	**CHKD3125T106W**	**CHKD3125T107W**	70	**ORPK125A70**
			90	**ORPK125A90**
			100	**ORPK125A100**
			110	**ORPK125A110**
			125	**ORPK125A125**
250	**CHKD3250T106W**	**CHKD3250T107W**	125	**ORPK025A125**
			150	**ORPK025A150**
			175	**ORPK025A175**
			200	**ORPK025A200**
			225	**ORPK025A225**
			250	**ORPK025A250**
400	**CHKD3400T106W**	**CHKD3400T107W**	200	**ORPK40A200**
			225	**ORPK40A225**
			250	**ORPK40A250**
			300	**ORPK40A300**
			350	**ORPK40A350**
			400	**ORPK40A400**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Factory sealed.

Accessories Selection Guide and Ordering Guide

Line and Load Terminals

Eaton's line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. All terminals comply with Underwriters Laboratories Standards UL 486A and UL 486B and CSA Standard C22.2 No. 65, or Electrical Bulletin 1165. Unless otherwise specified, K-Frame circuit breaker line and load terminals are shipped separately for field installation.

Ordering Information

K-Frame circuit breakers use Cu/Al terminals as standard. When optional copper or Cu/Al terminals are required, order by catalog number. Specify if factory installation is required.



TA401K



TA400K, T400K



TA350K, T350K



TA300K, T300K



Tab is 1/4 x.032

T400KCW, TA400KCW, TA401KCW



TA402K, T402K

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/No. Conductors	Metric Wire Range mm^2	Terminal Catalog Number	Terminals with Control Wire Termination Catalog Number
Standard Cu/Al Pressure Terminals						
225	Aluminum	Cu/Al	3–350 (1)	35–185	**TA300K** ①	—
400	Aluminum	Cu/Al	250–500 (1)	120–240	**TA350K** ①	—
400	Aluminum	Cu/Al	3/0–250 (2)	95–120	**2TA400K** ②③	**2TA400KCW** ②③
400	Aluminum	Cu/Al	3/0–250 (2)	95–120	**3TA400K** ②④	**3TA400KCW** ②④
400	Aluminum	Cu/Al	3/0–250 (2)	95–120	**4TA400K** ⑤⑥	**4TA400KCW** ⑤⑥
Optional Copper and Cu/Al Pressure Type Terminals						
225	Copper	Cu	3–350 (1)	35–185	**T300K**①	—
400	Copper	Cu	250–500 (1)	120–240	**T350K** ①	—
400	Copper	Cu	3/0–250 (2)	95–120	**2T400K** ③	**2T400KCW** ②③
					3T400K ④	**3T400KCW** ②④
					4T400K ⑤	**4T400KCW** ⑤⑥
400	Aluminum	Cu/Al	2/0–250 (2) or 2/0–500 (1)	70–120	**2TA401K** ②③	**2TA401KCW** ②③
				70–240	**3TA401K** ②④	**3TA401KCW** ②④
				70–240	**4TA401K** ⑤⑥	**4TA401KCW** ⑤⑥
400	Aluminum	Cu/Al	500–750 (1)	300–400	**2TA402K** ②③	—
					3TA402K ②④	—
					4TA402K ⑤⑥	—
400	Copper	Cu	500–750 (1)	—	**2T402K** ②③	—
					3T402K ②④	—
					4T402K ⑤⑥	—

Notes

① Individually packed.
② Terminal kits contain one terminal for each pole and one terminal cover.
③ Two-pole kit.
④ Three-pole kit.
⑤ Four-pole kit.
⑥ Terminal kits contain one terminal for each pole and three interphase barriers.

Accessories

Allowable Accessory Combinations

2

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

KD Frame Accessories

Description	Reference Page	Two-Pole ①		Three-Pole			Four-Pole			
		Left	Right	Left	Center	Right	Left	Center	Right	Neutral
Internal Accessories (Only One Internal Accessory Per Pole)										
Alarm lockout (Make/Break)	V4-T2-276		■	❑		❑	■			
Alarm lockout (2Make/2Break)	V4-T2-276			❑		❑	■			
Auxiliary switch (1A, 1B)	V4-T2-278		■	■		■	■		■	
Auxiliary switch (2A, 2B)	V4-T2-278			■		■	■		■	
Auxiliary switch (3A, 3B)	V4-T2-278			■		■	■		■	
Auxiliary switch and alarm switch combination	V4-T2-279			❑		❑	❑		❑	
Shunt trip—standard ②	V4-T2-282		■	■		■	■		■	
Shunt trip—low energy ②	V4-T2-285			■		■	■			
Undervoltage release mechanism ②	V4-T2-290		■	■		■	■			
PowerNet or zone interlock kit (OPTIM 550)	V4-T2-293					■				
External Accessories										
End cap kit	V4-T2-310	●	●	●	●	●	●	●	●	●
Keeper nut	V4-T2-310	●	●	●	●	●	●	●	●	●
Control wire terminal kit	V4-T2-311	●	●	●	●	●	●	●	●	●
Terminal adapter	V4-T2-311	●	●	●	●	●	●	●	●	●
Multiwire connectors	V4-T2-312	●	●	●	●	●	●	●	●	●
Rear fed terminals	V4-T2-312	●	●	●	●	●	●	●	●	●
Base mounting hardware	V4-T2-313	●	●	●	●	●	●	●	●	●
Terminal shields	V4-T2-315	●	●	●	●	●	●	●	●	●
Interphase barriers	V4-T2-315	●	●	●	●	●	●	●	●	●
Non-padlockable handle block	V4-T2-316	■			■			■		
Padlockable handle block	V4-T2-316				■					
Padlockable handle lock hasp	V4-T2-317		■	❑		❑	❑		❑	
Cylinder lock	V4-T2-317	❑	❑	❑		❑				
Key Interlock kit	V4-T2-318	■	❑	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	V4-T2-319			●	●	●				
Walking beam interlock—requires two breakers	V4-T2-319			●	●	●	●	●	●	●
Electrical (solenoid) operator	V4-T2-320			●	●	●	●	●	●	●
Plug-in adapters	V4-T2-321	●	●	●	●	●	●	●	●	●
Rear connecting studs	V4-T2-323	●	●	●	●	●	●	●	●	●
Panelboard connecting straps	V4-T2-324	●	●	●	●	●	●	●	●	●
Handle mechanisms	V4-T2-427	●	●	●	●	●	●	●	●	●
Handle extension	V4-T2-442	●	●	●	●	●	●	●	●	●
IQ Energy Sentinel	V4-T2-326			●	●	●	●	●	●	●
Solid-state (electronic) portable test kit	V4-T2-326	●	●	●	●	●	●	●	●	●
OPTIM System Components Three Poles										
Breaker interface module (BIM)	V4-T2-327									
Digitrip OPTIMizer	V4-T2-327									
Auxiliary power module	V4-T2-327									
Modifications (Refer to Eaton)										
Special calibration	—	●	●	●	●	●	●	●	●	●
Moisture fungus treatment	V4-T2-116	●	●	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Notes

① Two-pole breaker supplied in three-pole frame. Current carrying parts omitted from center pole.

② Shunt trip and UVR cannot be mounted in right poles on KES or OPTIM trip units. Standard internal accessories cannot be mounted in right pole on any K-Frame OPTIM trip unites. Special OPTIM ground fault and zone interlock accessories are available for field installation in the right pole of K-Frame 550 OPTIM trip units. Factory installed 2a/2b and bell/aux are available for factory installation. K-Frame breakers equipped with OPTIM 1050 trip units include aux-bell alarm in the right pole.

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V** ②
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor, 400 A	**LGFCT400** ③
External neutral sensor, 250 A	**LGFCT250** ③
External neutral sensor, 125 A	**LGFCT125** ③
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06** ④

Technical Data and Specifications

NEMA/UL 489/CSA Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600	Volts DC 250 ⑤⑥
DK	2, 3	65	—	—	—	10
KDB	2, 3, 4	65	—	35	25	10
KD	2, 3, 4	65	—	35	25	10
HKD, HKDB	2, 3, 4	100	—	65	35	22
KDC ⑦	2, 3, 4	200	—	100	65	22
CKD	3	65	—	35	25	—
CHKD	3	100	—	65	35	—

IEC 157-1 (P1) Interrupting Capacity Ratings

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	380	415	440	500	600	Volts DC 250 ⑤⑥
DK	2, 3	65	—	—	—	—	—	10
KDB	2, 3, 4	65	40	40	—	—	—	10
KD	2, 3, 4	65	40	40	—	—	—	10
HKD, HKDB	2, 3, 4	100	65	65	—	—	—	22
KDC	2, 3, 4	200	100	100	—	—	—	22

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
KDC	240 V/200 kA	56.00	2.30
KDC	480 V/100 kA	53.30	5.60
KDC	600 V/50 kA	43.40	5.40

Notes

① Two-pole breaker supplied in three-pole frame. Current carrying parts omitted from center pole.
② MTST230V applies to 100–230 Vac.
③ Included with all LD LSG and LSIG trip units and breakers.
④ Includes 6 ft cable for remote mounting; NEMA 3R rated.
⑤ Two-pole circuit breaker or two outside poles of three-pole circuit breaker.
⑥ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds minimum at 22 kA.
⑦ Current limiting.

310+ Specifications

Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame	K
Frames available	125 A, 250 A, 400 A
Continuous current range (A)	55–400 A
Ground fault pickup (A)	50–400 A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash Reduction Maintenance System	Remote enabled on ALSI, ALSIG
Interchangeable trip unit	Yes
High load alarm, trip (suffix B20) ①	Yes
Ground fault alarm with trip (suffix B21) ①	LSG, LSIG, ALSIG
Ground fault alarm, no trip (suffix B22)	LSG, LSIG, ALSIG
Zone selective interlock (suffix ZG) ①	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes (via TRIP-LED or DIGIVIEW)
Thru-cover accessories	No

310+ Adjustability Specifications

310+ Settings		K-Frame 125A	250 A	400 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	Ir \ In			
	A (=Ir)	55	100	160
	B (=Ir)	60	125	200
	C (=Ir)	70	150	225
	D (=Ir)	80	160	250
	E (=Ir)	90	175	300
	F (=Ir)	100	200	315
	G (=Ir)	110	225	350
	H (=Ir=In)	125	250	400
t_r = long delay time (seconds) (All 310+)	2	2	2	2
	4	4	4	4
	7	7	7	7
	10	10	10	10
	12	12	12	12
	15	15	15	15
	20	20	20	20
	24	24	24	24
I_{sd} (x I_r) = short delay pickup (amperes) (All 310+)	Position 1	2	2x	2x
	Position 2	3	3x	3x
	Position 3	4	4x	4x
	Position 4	5	5x	5x
	Position 5	6	6x	6x
	Position 6	7	7x	7x
	Position 7	8	8x	8x
	Position 8	10	10x	10x
	Position 9	12	12x	12x
t_{sd} = short delay time I^2t (milliseconds) (LS and LSG)	Fixed	67 @10x		
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG, ALSI, ALSIG)	Position 1	Inst		
	Position 2	120		
	Position 3	300		
I_g (x I_n) = ground fault pickup (amperes) (LSG, LSIG, ALSIG)	Position 1	25	50	80
	Position 2	37.5	75	120
	Position 3	50	100	160
	Position 4	75	150	240
	Position 5	100	200	320
	Position 6	125	250	400
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst		
	Position 2	120		
	Position 3	300		
Independently adjustable Instantaneous (Ii) setting	②			
Maintenance Mode pickup (2.5 x I_n) (amperes) (310+ with Maintenance Mode—ALSI and ALSIG)	Fixed	312	625	1000

Notes

① B2x suffixes cannot be combined with B2x suffixes.

② Not available for KD. Independently adjustable I_i setting available in LG, NG and RG ALSI and ALSIG trip units.

Specifications

Trip Unit Type	Digitrip OPTIM 550	Digitrip OPTIM 1050
rms sensing	Yes	Yes
Breaker Type		
Frame	K	K
Ampere range	125–400 A	125–400 A
Interrupting rating at 480 volts	35, 65, 100 (kA)	35, 65, 100 (kA)
Protection		
Ordering options	LSI, LSI(A), LSIG	LSI(A), LSIG
Fixed rated plug (I_n)	Yes	Yes
Overtemperature trip	Yes	Yes
Long Delay Protection (L)		
Adjustable rating plug (I_n)	No	No
Long delay pickup	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)
Long delay time I^2t	2–24 seconds	2–24 seconds
Long delay time I^4t	1–5 seconds	1–5 seconds
Long delay thermal memory	Yes	Yes
High load alarm	0.5–1.0 x I_r	0.5–1.0 x I_r
Short Delay Protection (S)		
Short delay pickup	150–800% x (I_r)	150–800% x (I_r)
Short delay time I^2t	100–500 ms	100–500 ms
Short delay time flat	100–500 ms	100–500 ms
Short delay time zone selective interlocking	Yes ①	Yes
Instantaneous Protection (I)		
Instantaneous pickup	200–800% x (I_n)	200–800% x (I_n)
Discriminator	Yes	Yes
Instantaneous override	Yes	Yes
Ground Fault Protection (G)		
Ground fault alarm	20–100% x (I_s)	20–100% x (I_s)
Ground fault pickup	20–100% x (I_s)	20–100% x (I_s)
Ground fault delay I^2t	100–500 ms	100–500 ms
Ground fault delay flat	100–500 ms	100–500 ms
Ground fault zone selective interlocking	Yes ①	Yes
Ground fault thermal memory	Yes	Yes
System Diagnostics		
Status LEDs	Yes	Yes
Cause of trip LEDs	Yes	Yes
Magnitude of trip information	Yes	Yes
Remote signal contact—ground alarm	Yes ①	Yes
Local auxiliary and bell alarm contact	Optional	Included
System Monitoring		
Digital display	Yes ②	Yes ②
Current	Yes	Yes
Power and energy	No	Yes
Power quality—harmonics	No	Yes
Power factor	No	Yes
Communications		
PowerNet	Yes ③	Yes
Testing		
Testing method	OPTIMizer, BIM, PowerNet	OPTIMizer, BIM, PowerNet

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting

Notes

① Zone interlock kit.
② By OPTIMizer/BIM.
③ Eaton's PowerNet kit.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

KD Frame

Number of Poles	Width	Height	Depth
2, 3	5.50 (149.7)	10.13 (257.3)	4.10 (104.1)
4	7.22 (183.4)	10.13 (257.3)	4.10 (104.1)

KD-Frame, Two- and Three-Pole



Approximate Shipping Weight, Lbs (kg)

KD Frame

Breaker Type	Complete Breaker		Frame Only		Trip Unit ①	
	Two-Pole	Three-Pole	Two-Pole	Three-Pole	Two-Pole	Three-Pole
DK	10.0 (4.5)	11.5 (5.2)	—	—	—	—
KDB	10.0 (4.5)	11.5 (5.2)	—	—	—	—
KD	10.0 (4.5)	11.5 (5.2)	7.5 (3.4)	8.5 (3.9)	1.5 (0.7)	1.5 (0.7)
HKD, HKDB	10.0 (4.5)	11.5 (5.2)	7.5 (3.4)	8.5 (3.9)	1.5 (0.7)	1.5 (0.7)
KDC	10.0 (4.5)	11.5 (5.2)	7.5 (3.4)	8.5 (3.9)	1.5 (0.7)	1.5 (0.7)

Note

① Weights shown are for thermal-magnetic trip units. Three-pole electronic trip units weigh 2.5 lbs (1.1 kg).

Typical L-Frame Circuit Breaker

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	
Catalog Number Selection	**V4-T2-186**
Product Selection	**V4-T2-188**
Accessories	**V4-T2-204**
Technical Data and Specifications	**V4-T2-206**
Dimensions and Weights	**V4-T2-210**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

L-Frame (125–600 Amperes)

Product Description

- All Eaton L-Frame circuit breakers are HACR rated
- L-Frame circuit breakers are available as individual components (frame, trip unit, terminals), or factory assembled complete breakers
- L-Frame circuit breakers with non-interchangeable trip units are suitable for reverse feed use

Standards and Certifications

- CE marked

CE

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

2

LD-Frame with Thermal-Magnetic Trip Unit Technology

Thermal-Magnetic Breakers and Frame ①



Thermal-Magnetic Trip Unit ①



Note

① Frames are the same for thermal-magnetic or 310+ electronic trip units, e.g., **LD3600F**, **HLD3600F**, etc.

LD-Frame with 310+ Electronic Trip Unit Technology

310+ Circuit Breakers

LDB 3 600 F T36 B22ZG W

Performance at 480 Vac	
LDB	= 35 kAIC
HLDB	= 65 kAIC
LDCB	= 100 kAIC
CLDB	= 35 kAIC, 100% rated
CHLDB	= 65 kAIC, 100% rated
CLDCB	= 100 kAIC, 100% rated

Number of Poles
3 = Three-pole
4 = Four-pole

Amperes
600

Designation
F

Trip Unit	
T33	= 310+ Electronic LS
T32	= 310+ Electronic LSI
T35	= 310+ Electronic LSG ①
T36	= 310+ Electronic LSIG ①
T38	= 310+ Electronic LSI with Maintenance Mode
T39	= 310+ Electronic LSIG with Maintenance Mode ①

Features	
Blank	= No feature
B20	= High load alarm
B21	= Ground fault alarm, with trip ①
B22	= Ground fault alarm, no trip ①
ZG	= Zone selective interlocking

Terminals
W = No terminals

310+ Electronic Trip Units ②

LES 3 600 LSIG B22ZG

Trip Unit Type
LES

Number of Poles
3 = Three-pole
4 = Four-pole

Amperes
600

Trip Unit	
LS	= 310+ Electronic LS
LSI	= 310+ Electronic LSI
LSG	= 310+ Electronic LSG ①
LSIG	= 310+ Electronic LSIG ①
ALSI	= 310+ Electronic LSI with Maintenance Mode
ALSIG	= 310+ Electronic LSIG with Maintenance Mode ①

Features	
Blank	= No feature
B20	= High load alarm
B21	= Ground fault alarm, with trip ①
B22	= Ground fault alarm, no trip ①
ZG	= Zone selective interlocking

LD-Frame with OPTIM Electronic Trip Unit Technology

OPTIM Circuit Breakers

LD 3 125 T5 7 W

Circuit Breaker/ Frame Type
LD
HLD
LDC
CLD
CHLD
CLDC

Number of Poles
3 = Three-pole

Circuit Breaker/ Frame Ampere Rating
125 (Available on Model 1050 only)
250 (Available on Model 1050 only)
400
600

Trip Model
T5 = Model 550
T10 = Model 1050

Trip Type
2 = LSI (550 only)
6 = LSIG
7 = LSIA

Suffix
W = Without terminals

Notes

① Not available in four-pole configurations.

② Frames are the same for thermal-magnetic or 310+ electronic trip units, e.g., **LD3600F**, **HLD3600F**, etc.

Product Selection

Types LD, HLD and LDC Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40 °C ①	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Thermal-Magnetic Trip Unit Only For Use with Standard or High or Ultra High Interrupting Frames Catalog Number	Standard Terminals Only See Page V4-T2-203 for Optional Terminals Catalog Number
Two-Pole					
300	**LD2300**	**HLD2300**	**LDC2300**	**LT2300T**	**TA602LD** ②
350	**LD2350**	**HLD2350**	**LDC2350**	**LT2350T**	**TA602LD** ②
400	**LD2400**	**HLD2400**	**LDC2400**	**LT2400T**	**TA602LD** ②
450	**LD2450**	**HLD2450**	**LDC2450**	**LT2450T**	**TA602LD** ②
500	**LD2500**	**HLD2500**	**LDC2500**	**LT2500T**	**TA602LD** ②
600	**LD2600**	**HLD2600**	**LDC2600**	**LT2600T**	**2TA603LDK** ③
Three-Pole					
300	**LD3300**	**HLD3300**	**LDC3300**	**LT3300T**	**TA602LD** ②
350	**LD3350**	**HLD3350**	**LDC3350**	**LT3350T**	**TA602LD** ②
400	**LD3400**	**HLD3400**	**LDC3400**	**LT3400T**	**TA602LD** ②
450	**LD3450**	**HLD3450**	**LDC3450**	**LT3450T**	**TA602LD** ②
500	**LD3500**	**HLD3500**	**LDC3500**	**LT3500T**	**TA602LD** ②
600	**LD3600**	**HLD3600**	**LDC3600**	**LT3600T**	**3TA603LDK** ③
Four-Pole ④					
300	**LD4300**	**HLD4300**	**LDC4300**	**LT4300T**	**TA602LD** ②
350	**LD4350**	**HLD4350**	**LDC4350**	**LT4350T**	**TA602LD** ②
400	**LD4400**	**HLD4400**	**LDC4400**	**LT4400T**	**TA602LD** ②
450	**LD4450**	**HLD4450**	**LDC4450**	**LT4450T**	**TA602LD** ②
500	**LD4500**	**HLD4500**	**LDC4500**	**LT4500T**	**TA602LD** ②
600	**LD4600**	**HLD4600**	**LDC4600**	**LT4600T**	**4TA603LDK** ③

Types LD, HLD and LDC Thermal-Magnetic Circuit Breakers—Frame Only

Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Catalog Number	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac Catalog Number
Two-Pole		
LD2600F	**HLD2600F**	**LDC2600F**
Three-Pole		
LD3600F	**HLD3600F**	**LDC3600F**
Four-Pole		
LD4600F	**HLD4600F**	**LDC4600F**

Notes

① Magnetic trip range 5–10 times continuous ampere rating.
② Individually packed.
③ Terminal kits contain one terminal for each pole and one terminal cover.
④ Neutral is in right pole.

Types LD, HLD and LDC Electronic Circuit Breakers with Interchangeable Trip Units

Order as individual components: breaker frame, trip unit and terminals. See 310+ adjustability specifications on **Page V4-T2-182**.

Types LD, HLD and LDC Electronic Circuit Breakers with Interchangeable 310+ Trip Units

	Circuit Breaker Frame Only			Digitrip RMS 310+ Trip Unit Only ①					
				Standard LS	Optional LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③	Terminal Information
	Catalog Number			Catalog Number				Catalog Number	
Three-Pole									
600	**LD3600F**	**HLD3600F**	**LDC3600F**	**LES3600LS**	**LES3600LSI**	**LES3600LSG**	**LES3600LSIG**	**LGFCT600**	See **Page V4-T2-180**
Four-Pole ④									
600	**LD4600F**	**HLD4600F**	**LDC4600F**	**LES4600LS**	**LES4600LSI**	—	—	—	See **Page V4-T2-180**

Types LDB, HLDB and LDCB Electronic Circuit Breakers with Non-Interchangeable 310+ Electronic Trip Units Suitable for Reverse Feed

See 310+ adjustability specifications on **Page V4-T2-182**.

Circuit Breaker Frame Including Digitrip RMS 310+ Electronic Trip Unit Less Terminals Types LDB, HLDB and LDCB with Digitrip 310+ Non-Interchangeable Trip Units

		Factory Assembled Circuit Breaker Consisting of Frame and Trip Unit Less Terminals ①						
		Standard LS	Optional LSI	LSG	LSIG			
Maximum Continuous Ampere Rating at 40 °C	Number of Poles	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③	Terminal Information
		Catalog Number				Catalog Number	
600	**3**	**LDB3600FT33W**	**LDB3600FT32W**	**LDB3600FT35W**	**LDB3600FT36W**	**LGFCT600**	See **Page V4-T2-180**
600	**3**	**HLDB3600FT33W**	**HLDB3600FT32W**	**HLDB3600FT35W**	**HLDB3600FT36W**		
600	**3**	**LDCB3600FT33W**	**LDCB3600FT32W**	**LDCB3600FT35W**	**LDCB3600FT36W**		

100% Rated Types CLD, CHLD and CLDC Electronic Circuit Breakers with Interchangeable Trip Units

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at the 75 °C ampacity. All 100% rated circuit breakers have electronic trip units. Order as individual components: breaker frame, trip unit and terminals. See 310+ adjustability specifications on **Page V4-T2-182**.

100% Rated Types CLD, CHLD and CLDC Electronic Circuit Breakers with 310+ Interchangeable Trip Units

	Circuit Breaker Frame Only			Digitrip RMS 310+ Trip Unit Only					
				Standard LS	Optional LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③	Terminal Information
	Catalog Number			Catalog Number				Catalog Number	
Three-Pole									
600	**CLD3600F**	**CHLD3600F**	**CLDC3600F**	**LES3600LS**	**LES3600LSI**	**LES3600LSG**	**LES3600LSIG**	**LGFCT600**	See **Page V4-T2-180**

Notes

① For AC use only.
② Required for four-wire systems if neutral protection is desired.
③ Included with LSG and LSIG trip units.
④ Neutral is in right pole.

Type LDB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units ①

Maximum Continuous Ampere Rating	600 Vac Rated, 250 Vdc Complete Circuit Breaker Without Line and Load Terminals Catalog Number	With Standard Line and Load Terminals Only Catalog Number
Two-Pole		
300	**LDB2300W**	**LDB2300**
350	**LDB2350W**	**LDB2350**
400	**LDB2400W**	**LDB2400**
450	**LDB2450W**	**LDB2450**
500	**LDB2500W**	**LDB2500**
600	**LDB2600W**	**LDB2600**
Three-Pole		
300	**LDB3300W**	**LDB3300**
350	**LDB3350W**	**LDB3350**
400	**LDB3400W**	**LDB3400**
450	**LDB3450W**	**LDB3450**
500	**LDB3500W**	**LDB3500**
600	**LDB3600W**	**LDB3600**

Molded Case Switches

Eaton's molded case switches are used as compact switches in applications requiring high current switching capabilities. Molded case switches are constructed of circuit breaker components and are of the high instantaneous automatic type. Molded case switches are listed in accordance with Underwriters Laboratories Standard UL 489.

Molded Case Switches

Maximum Continuous Ampere Rating at 40 °C	600 Vac Maximum, 250 Vdc Circuit Breaker Only without Line and Load Terminals Catalog Number	Standard Terminals Only See Page V4-T2-203 for Optional Terminals Catalog Number
Two-Pole		
600	**LD2600WK**	**2TA603LDK**
600	**LDB2600WK** ①	**2TA603LDK**
600	**HLD2600WK**	**2TA603LDK**
Three-Pole		
600	**LD3600WK**	**3TA603LDK**
600	**LDB3600WK** ①	**3TA603LDK**
600	**HLD3600WK**	**3TA603LDK**
Four-Pole		
600	**LD4600WK**	**4TA603LDK**
600	**LDB4600WK** ①	**4TA603LDK**
600	**HLD4600WK**	**4TA603LDK**

Notes

① Factory sealed—suitable for reverse feed application.

Molded case switch will trip above 6000 amperes.

Digitrip OPTIM Electronic Circuit Breaker with Interchangeable Rating Plug

Order as individual components: Breaker Frame (which includes Trip Unit), Rating Plug, Terminals.

Digitrip OPTIM 550 Electronic Circuit Breaker with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				Fixed Rating Plug
	LSI	LSIG	LSIA		
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac					
125	**LD3125T52W**	**LD3125T56W**	**LD3125T57W**	—	**ORPL125A070**
				—	**ORPL125A090**
				—	**ORPL125A100**
				—	**ORPL125A110**
				—	**ORPL125A125**
250	**LD3250T52W**	**LD3250T56W**	**LD3250T57W**	—	**ORPL025A125**
				—	**ORPL025A150**
				—	**ORPL025A175**
				—	**ORPL025A200**
				—	**ORPL025A225**
				—	**ORPL025A250**
400	**LD3400T52W**	**LD3400T56W**	**LD3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				300	**ORPL40A300**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**LD3600T52W**	**LD3600T56W**	**LD3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 550 Electronic Circuit Breaker with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				
	LSI	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
125	**HLD3125T52W**	**HLD3125T56W**	**HLD3125T57W**	70	**ORPL125A070**
				90	**ORPL125A090**
				100	**ORPL125A100**
				110	**ORPL125A110**
				125	**ORPL125A125**
250	**HLD3250T52W**	**HLD3250T56W**	**HLD3250T57W**	125	**ORPL025A125**
				150	**ORPL025A150**
				175	**ORPL025A175**
				200	**ORPL025A200**
				225	**ORPL025A225**
				250	**ORPL025A250**
400	**HLD3400T52W**	**HLD3400T56W**	**HLD3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				300	**ORPL40A300**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**HLD3600T52W**	**HLD3600T56W**	**HLD3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 550 Electronic Circuit Breaker with Interchangeable Rating Plug, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac					
125	**LDC3125T52W**	**LDC3125T56W**	**LDC3125T57W**	—	**ORPL125A070**
				—	**ORPL125A090**
				—	**ORPL125A100**
				—	**ORPL125A110**
				—	**ORPL125A125**
250	**LDC3250T52W**	**LDC3250T56W**	**LDC3250T57W**	—	**ORPL025A125**
				—	**ORPL025A150**
				—	**ORPL025A175**
				—	**ORPL025A200**
				—	**ORPL025A225**
				—	**ORPL025A250**
400	**LDC3400T52W**	**LDC3400T56W**	**LDC3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				300	**ORPL40A300**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**LDC3600T52W**	**LDC3600T56W**	**LDC3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM Electronic Circuit Breaker with Interchangeable Rating Plug

Order as individual components: Breaker Frame (which includes Trip Unit), Rating Plug, Terminals.

2

Digitrip OPTIM 1050 Electronic Circuit Breaker with Interchangeable Rating Plug

	Circuit Breaker Frame Only		Digitrip OPTIM Rating Plug Only	
	L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac				
125	**LD3125T106W**	**LD3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**LD3250T106W**	**LD3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**LD3400T106W**	**LD3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**LD3600T106W**	**LD3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.
③ Factory sealed.

Digitrip OPTIM 1050 Electronic Circuit Breaker with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
125	**HLD3125T106W**	**HLD3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**HLD3250T106W**	**HLD3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**HLD3400T106W**	**HLD3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**HLD3600T106W**	**HLD3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.
③ Factory sealed.

Digitrip OPTIM 1050 Electronic Circuit Breaker with Interchangeable Rating Plug, continued

	Circuit Breaker Frame Only		Digitrip OPTIM Rating Plug Only	
	L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			
Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac				
125	**LDC3125T106W**	**LDC3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**LDC3250T106W**	**LDC3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**LDC3400T106W**	**LDC3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**LDC3600T106W**	**LDC3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.

③ Factory sealed.

100% Rated Digitrip OPTIM Circuit Breakers with Interchangeable Rating Plug

Order as individual components: Breaker Frame (which includes Trip Unit), Rating Plug, Terminals.

100% Rated Digitrip OPTIM 550 Circuit Breakers with Interchangeable Rating Plug

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ②				Fixed Rating Plug
	LSI	LSIG	LSIA		
	Catalog Number	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac					
125	**CLD3125T52W**	**CLD3125T56W**	**CLD3125T57W**	70	**ORPL125A070**
				90	**ORPL125A090**
				100	**ORPL125A100**
				110	**ORPL125A110**
				125	**ORPL125A125**
250	**CLD3250T52W**	**CLD3250T56W**	**CLD3250T57W**	125	**ORPL025A125**
				150	**ORPL025A150**
				175	**ORPL025A175**
				200	**ORPL025A200**
				225	**ORPL025A225**
				250	**ORPL025A250**
400	**CLD3400T52W**	**CLD3400T56W**	**CLD3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				300	**ORPL40A300**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**CLD3600T52W**	**CLD3600T56W**	**CLD3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

100% Rated Digitrip OPTIM 550 Circuit Breakers with Interchangeable Rating Plug, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Fixed Rating Plug Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
125	**CHLD3125T52W**	**CHLD3125T56W**	**CHLD3125T57W**	70	**ORPL125A070**
				90	**ORPL125A090**
				100	**ORPL125A100**
				110	**ORPL125A125**
				125	**ORPL125A125**
250	**CHLD3250T52W**	**CHLD3250T56W**	**CHLD3250T57W**	125	**ORPL025A125**
				150	**ORPL025A150**
				175	**ORPL025A175**
				200	**ORPL025A200**
				225	**ORPL025A225**
				250	**ORPL025A250**
400	**CHLD3400T52W**	**CHLD3400T56W**	**CHLD3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**CHLD3600T52W**	**CHLD3600T56W**	**CHLD3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

100% Rated Digitrip OPTIM 550 Circuit Breakers with Interchangeable Rating Plug, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac					
125	**CLDC3125T52W**	**CLDC3125T56W**	**CLDC3125T57W**	70	**ORPL125A070**
				90	**ORPL125A090**
				100	**ORPL125A100**
				110	**ORPL125A110**
				125	**ORPL125A125**
250	**CLDC3250T52W**	**CLDC3250T56W**	**CLDC3250T57W**	125	**ORPL025A125**
				150	**ORPL025A150**
				175	**ORPL025A175**
				200	**ORPL025A200**
				225	**ORPL025A225**
				250	**ORPL025A250**
400	**CLDC3400T52W**	**CLDC3400T56W**	**CLDC3400T57W**	200	**ORPL40A200**
				225	**ORPL40A225**
				250	**ORPL40A250**
				300	**ORPL40A300**
				350	**ORPL40A350**
				400	**ORPL40A400**
600	**CLDC3600T52W**	**CLDC3600T56W**	**CLDC3600T57W**	300	**ORPL60A300**
				350	**ORPL60A350**
				400	**ORPL60A400**
				500	**ORPL60A500**
				600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

100% Rated Digitrip OPTIM 1050 Circuit Breakers with Interchangeable Rating Plug

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Fixed Rating Plug Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 35 kAIC at 480 Vac				
125	**CLD3125T106W**	**CLD3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**CLD3250T106W**	**CLD3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**CLD3400T106W**	**CLD3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**CLD3600T106W**	**CLD3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.
③ Factory sealed.

100% Rated Digitrip OPTIM 1050 Circuit Breakers with Interchangeable Rating Plug, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Fixed Rating Plug Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
125	**CHLD3125T106W**	**CHLD3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**CHLD3250T106W**	**CHLD3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**CHLD3400T106W**	**CHLD3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**CHLD3600T106W**	**CHLD3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.
③ Factory sealed.

100% Rated Digitrip OPTIM 1050 Electronic Circuit Breaker with Interchangeable Rating Plug, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity Current Limiting 600 Vac Rated 100 kAIC at 480 Vac				
125	**CLDC3125T106W**	**CLDC3125T107W**	70	**ORPL125A070**
			90	**ORPL125A090**
			100	**ORPL125A100**
			110	**ORPL125A110**
			125	**ORPL125A125**
250	**CLDC3250T106W**	**CLDC3250T107W**	125	**ORPL025A125**
			150	**ORPL025A150**
			175	**ORPL025A175**
			200	**ORPL025A200**
			225	**ORPL025A225**
			250	**ORPL025A250**
400	**CLDC3400T106W**	**CLDC3400T107W**	200	**ORPL40A200**
			225	**ORPL40A225**
			250	**ORPL40A250**
			300	**ORPL40A300**
			350	**ORPL40A350**
			400	**ORPL40A400**
600	**CLDC3600T106W**	**CLDC3600T107W**	300	**ORPL60A300**
			350	**ORPL60A350**
			400	**ORPL60A400**
			500	**ORPL60A500**
			600	**ORPL60A600**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell alarm switch supplied with breaker as standard.
③ Factory sealed.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

Eaton's line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. All terminals comply with Underwriters Laboratories Standards UL 486A and UL 486B and CSA Standard C22.2 No. 65M. Unless otherwise specified, L-Frame circuit breaker line and load terminals are shipped separately for field installation.

The wire connecting terminal is secured with two pan-head, slotted screws and lockwashers that can be checked for the correct torque loading or retightened from the front of the circuit breaker before installation of the conductors. (Applies to all styles.) The circuit breaker line/load terminal conductors are positioned in the conducting holes in the wire connecting terminal and are secured with recessed socket screws that are tightened to the correct torque loading from the front of the circuit breaker.

Ordering Information

L-Frame circuit breakers use Cu/Al terminals as standard. When optional copper terminals are required, order by catalog Number. Specify if factory installation is required.

Terminals



Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/Number of Conductors	Metric Wire Range mm²	Terminal Poles	Catalog Number	Terminals with Control Wire Termination Catalog Number
Standard Cu/Al Pressure Terminals							
400	Aluminum	Cu/Al	4/0–600 (1)	120–300	Two-pole kit ①	**2TA401LDK**	—
400	Aluminum	Cu/Al	4/0–600 (1)	120–300	Three-pole kit ①	**3TA401LDK**	—
400	Aluminum	Cu/Al	4/0–600 (1)	120–300	Four-pole kit ①	**4TA401LDK**	—
450	Aluminum	Cu/Al	4–4/0 (2)	25–95	②	**TA450LD**	—
500	Aluminum	Cu/Al	3/0–350 (2)	95–150	②	**TA602LD**	**TA602LDCW**
600	Aluminum	Cu/Al	400–500 (2)	185–240	Two-pole kit ①	**2TA603LDK**	**2TA603LDKCW**
600	Aluminum	Cu/Al	400–500 (2)	185–240	Three-pole kit ①	**3TA603LDK**	**3TA603LDKCW**
600	Aluminum	Cu/Al	400–500 (2)	185–240	Four-pole kit ①	**4TA603LDK**	**4TA603LDKCW**
Optional Copper and Cu/Al Pressure Type Terminals							
600	Copper	Cu	250–350 (2)	120–250	②	**T602LD**	**T602LDCW**

Notes

① Terminal kits contain one terminal for each pole and one terminal cover.

② Individually packed.

Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

LD Frame Accessories

Description	Reference Page	Two-Pole ①, Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neutral ②
Internal Accessories (Only One Internal Accessory Per Pole) ③								
Alarm lockout (Make/Break)	**V4-T2-276**	■		■	■		■	
Alarm lockout (2Make/2Break)	**V4-T2-276**	■		■	■		■	
Auxiliary switch (1A, 1B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (2A, 2B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (3A, 3B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (1A, 1B) and alarm switch combination	**V4-T2-280**	■		■	■		■	
Auxiliary switch (2A, 2B) and alarm switch combination	**V4-T2-280**	■		■	■		■	
Shunt trip—standard ④	**V4-T2-282**	■		■	■		■	
Shunt trip—low energy ④	**V4-T2-285**	■		■	■		■	
Undervoltage release mechanism ④	**V4-T2-291**	■		■	■		■	
Eaton PowerNet communications kit (OPTIM 550)	**V4-T2-293**			■				
External Accessories								
End cap kit	**V4-T2-310**	●	●	●	●	●	●	●
Control wire terminal kit	**V4-T2-311**	●	●	●	●	●	●	●
Base mounting hardware	**V4-T2-313**	●	●	●	●	●	●	●
Terminal shields	**V4-T2-315**	●	●	●	●	●	●	●
Interphase barriers	**V4-T2-315**	●	●	●	●	●	●	●
Non-padlockable handle block	**V4-T2-316**		■			■		
Padlockable handle lock hasp	**V4-T2-317**	❑		❑	❑		❑	
Key interlock kit	**V4-T2-318**	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-319**	●	●	●				
Walking beam interlock—requires two breakers	**V4-T2-319**	●	●	●	●	●	●	●
Electrical (motor) operator	**V4-T2-320**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-322**	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-323**	●	●	●	●	●	●	●
Panelboard connecting straps	**V4-T2-324**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-427**	●	●	●	●	●	●	●
Handle extension	**V4-T2-442**	●	●	●	●	●	●	●
Solid-state (electronic) portable test kit	**V4-T2-326**	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position
❑ May be mounted on left or right pole—not both
● Accessory available/modification available

Notes

① Two-pole breaker supplied in three-pole frame. Current carrying parts omitted from center pole.
② Refer to Eaton for appropriate neutral pole accessory combinations.
③ OPTIM model 1050 is factory sealed and does not have the right pole space available for accessories.
④ Shunt trip and UVR cannot be mounted in right poles on LES or OPTIM trip units. Standard non-tripping internal accessories can be mounted in the left or right poles of LES and 550 OPTIM trip units.

LD Frame Accessories, continued

Description	Reference Page	Two-Pole ①, Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neutral ②
OPTIM System Components Three Poles								
Ground fault alarm unit	**V4-T2-326**							
Potential transformer module	**V4-T2-326**							
Breaker interface module (BIM)	**V4-T2-327**							
Digitrip OPTIMizer	**V4-T2-327**							
Auxiliary power module	**V4-T2-327**							
Modifications (Refer to Eaton)								
Special calibration	—	●	●	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position

❑ May be mounted on left or right pole—not both

● Accessory available/modification available

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V** ③
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor	**LGFCT600** ④
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06** ⑤

Notes

① Two-pole breaker supplied in three-pole frame. Current carrying parts omitted from center pole.

② Refer to Eaton for appropriate neutral pole accessory combinations.

③ MTST230V applies to 100–230 Vac.

④ Included with all LD LSG and LSIG trip units and breakers.

⑤ Includes 6 ft cable for remote mounting; NEMA 3R rated.

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA rms Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600	Volts DC 125	250 ②③
LDB	2, 3	65	—	35	25	—	22
LD	2, 3, 4	65	—	35	25	—	22
CLD ④	2, 3, 4	65	—	35	25	—	—
HLD, HLDB	2, 3, 4	100	—	65	35	—	25
CHLD ④	2, 3, 4	100	—	65	35	—	—
LDC, LDCB ⑤	2, 3, 4	200	—	100	50	—	30
CLDC ④⑤	2, 3, 4	200	—	100	50	—	—

IEC 947-2 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240 I_{cu}	240 I_{cs}	415 I_{cu}	415 I_{cs}	690 I_{cu}	690 I_{cs}	Volts DC 250 ②③ I_{cu}	250 ②③ I_{cs}
LDB	2, 3	85	85	45	45	20	10	20	10
LD	2, 3, 4	85	85	45	45	20	10	20	10
CLD ④	2, 3, 4	85	85	45	45	20	10	—	—
HLD, HLDB	2, 3, 4	100	100	70	70	25	13	20	10
CHLD ④	2, 3, 4	100	100	70	70	25	13	—	—
LDC, LDCB	2, 3, 4	200	100	100	75	35	18	20	10
CLDC ④	2, 3, 4	200	100	100	75	35	18	—	—

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
LDC	240 V/200 kA	64.80	6.80
LDC	480 V/100 kA	66.90	9.33
LDC	600 V/50 kA	54.30	8.92

Notes

① Utilization Category A circuit breakers.
② L/R = 8 milliseconds minimum.
③ Two-pole circuit breaker or two poles of three-pole circuit breaker. Incorporating thermal-magnetic trip unit only.
④ 100% rated breakers.
⑤ Current limiting.

310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	LD
Frames available	600 A
Continuous current range (A)	250–600 A
Ground fault pickup (A)	120–600 A
Interrupting capacities at 480 Vac (kAIC)	35, 65, 100
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash Reduction Maintenance System (or Maintenance Mode)	Remote enabled on ALSI, ALSIG
Interchangeable trip unit	Yes
High load alarm (suffix B20) ①	Yes
Ground fault alarm with trip (suffix B21) ①	LSG, LSIG, ALSIG
Ground fault alarm, no trip (suffix B22) ①	LSG, LSIG, ALSIG
Zone selective interlocking (suffix ZG)	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes (via TRIP-LED or DIGIVIEW)
Thru-cover accessories	No

310+ Adjustability Specifications

Description		LD Frame Specification
310+ settings		600 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r	
	A	250
	B	300
	C	315
	D	350
	E	400
	F	450
	G	500
	H (= I_n)	600
t_r = long delay time (seconds) (All 310+)	2	2
	4	4
	7	7
	10	10
	12	12
	15	15
	20	20
	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x
	Position 2	3x
	Position 3	4x
	Position 4	5x
	Position 5	6x
	Position 6	7x
	Position 7	8x
	Position 8	8x
	Position 9	8x
t_{sd} = short delay time I^2t (milliseconds) (LS and LSG)	Fixed	67 @10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG, ALSI, ALSIG)	Position 1	Inst
	Position 2	120
	Position 3	300
I_g (x I_n) = ground fault pickup (amperes) (LSG, LSIG, ALSIG)	Position 1	120
	Position 2	180
	Position 3	240
	Position 4	360
	Position 5	480
	Position 6	600
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst
	Position 2	120
	Position 3	300
Independently adjustable Instantaneous (Ii) setting	②	
Maintenance Mode pickup (2.5 x I_n) (amperes) (310+ with Maintenance Mode—ALSI and ALSIG)	Fixed	1500

Notes

① B2x suffixes cannot be combined with B2x suffixes.

② Not available for LD. Independently adjustable Ii setting available in LG, NG, and RG ALSI and ALSIG trip units.

Digitrip OPTIM Specifications

Trip Unit Type	Digitrip OPTIM 550	Digitrip OPTIM 1050
rms sensing	Yes	Yes
Breaker Type		
Frame	L	L
Ampere range	200–600 A	200–600 A
Interrupting rating at 480 volts	35, 65, 100 (kA)	35, 65, 100 (kA)
Protection		
Ordering options	LSI, LSI(A), LSIG	LSI(A), LSIG
Fixed rated plug (I_n)	Yes	Yes
Overtemperature trip	Yes	Yes
Long Delay Protection (L)		
Adjustable rating plug (I_n)	No	No
Long delay pickup	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)
Long delay time I^2t	2–24 seconds	2–24 seconds
Long delay time I^4t	1–5 seconds	1–5 seconds
Long delay thermal memory	Yes	Yes
High load alarm	0.5–1.0 x I_r	0.5–1.0 x I_r
Short Delay Protection (S)		
Short delay pickup	150–800% x (I_r)	150–800% x (I_r)
Short delay time I^2t	100–500 ms	100–500 ms
Short delay time flat	100–500 ms	100–500 ms
Short delay time zone selective interlocking	Yes ①	Yes
Instantaneous Protection (I)		
Instantaneous pickup	200–800% x (I_n)	200–800% x (I_n)
Discriminator	Yes	Yes
Instantaneous override	Yes	Yes
Ground Fault Protection (G)		
Ground fault alarm	20–100% x (I_s)	20–100% x (I_s)
Ground fault pickup	20–100% x (I_s)	20–100% x (I_s)
Ground fault delay I^2t	100–500 ms	100–500 ms
Ground fault delay flat	100–500 ms	100–500 ms
Ground fault zone selective interlocking	Yes ①	Yes
Ground fault thermal memory	Yes	Yes

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting

Note

① Zone interlock kit.

Digitrip OPTIM Specifications, continued

Trip Unit Type	Digitrip OPTIM 550	Digitrip OPTIM 1050
System Diagnostics		
Status LEDs	Yes	Yes
Cause of trip LEDs	Yes	Yes
Magnitude of trip information	Yes	Yes
Remote signal contact—ground alarm	Yes ①	Yes
Local auxiliary and bell alarm contact	Optional	Included
System Monitoring		
Digital display	Yes ②	Yes ②
Current	Yes	Yes
Power and energy	No	Yes
Power quality—harmonics	No	Yes
Power factor	No	Yes
Communications		
PowerNet	Yes ③	Yes
Testing		
Testing method	OPTIMizer, BIM, PowerNet	OPTIMizer, BIM, PowerNet

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting

Notes

① Zone interlock kit.
② By OPTIMizer/BIM.
③ Eaton's PowerNet kit.

Dimensions and Weights

Dimensions in Inches (mm)

2

LD Frame

Number of Poles	Width	Height	Depth
2, 3	8.25 (209.6)	10.75 (273.1)	4.06 (103.1)
4	11.00 (279.4)	10.75 (273.1)	4.06 (103.1)

LD-Frame, Two- and Three-Pole

Front Cover Cutout



Front View



Side View



Approximate Shipping Weight, Lbs (kg)

LD Frame

Breaker Type	Complete Breaker			Frame Only			Trip Unit		
	Two-Pole	Three-Pole	Four-Pole	Two-Pole	Three-Pole	Four-Pole	Two-Pole	Three-Pole	Four-Pole
LD, HLD, LDC	18 (8.2)	20 (9.1)	25 (11.3)	14 (6.4)	15 (6.8)	20 (9.1)	3 (1.4)	4 (1.8)	5 (2.3)
LDB	18 (8.2)	20 (9.1)	25 (11.3)	—	—	—	—	—	—

Typical M-Frame Circuit Breaker

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	
Catalog Number Selection	**V4-T2-212**
Product Selection	**V4-T2-213**
Accessories	**V4-T2-218**
Technical Data and Specifications	**V4-T2-219**
Dimensions and Weights	**V4-T2-221**
Motor Circuit Protectors (MCP)	**V4-T2-256**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

M-Frame (300–800 Amperes)

Product Description

- All Eaton M-Frame circuit breakers are HACR rated
- MDL-Frame circuit breakers are available as individual components (frame, trip unit, terminals), or factory assembled complete breakers
- MDLB, HMDLB-Frame circuit breakers with non-interchangeable trip units are suitable for reverse feed use

Standards and Certifications

- CE marked

CE

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

2

MDL Frame with Thermal-Magnetic Trip Unit Technology

Thermal-Magnetic Breakers and Frame ①

MDL 3 800 F

Circuit Breaker/ Frame Type
MDL, MDLB
HMDL, HMDLB

Number of Poles
2 = Two-pole
3 = Three-pole

Circuit Breaker/ Frame Ampere Rating	
300 ①	**500**
350 ①	**600**
400	**700**
450	**800**

Suffix	
F	= Frame only (800 A only)
K	= High magnetic molded case switch
V	= 50 °C (thermal-magnetic trip units only)
W	= Without terminals
X	= Load side terminals only
Y	= Line side terminals only

Thermal-Magnetic Trip Unit ①

MT 3 800 T

Trip Unit Type
MT

Number of Poles
2 = Two-pole
3 = Three-pole

Trip Unit Rating/ Plug Ampere Rating	
300 ①	**500**
350 ①	**600**
400	**700**
450	**800**

Suffix	
T	= Thermal-magnetic
V	= 50 °C (thermal-magnetic trip units only)

MDL Frame with 310+ Electronic Trip Unit Technology

310+ Circuit Breaker

MDLB 3 800 F T36 B21 W

Performance at 480 Vac	
MDLB	= 50 kAIC
HMDLB	= 65 kAIC
CMDLB	= 50 kAIC, 100% rated
CHMDLB	= 65 kAIC, 100% rated

Number of Poles
3 = Three-pole

Amperes
800

Designation
F

Trip Unit	
T33	= 310+ Electronic LS
T32	= 310+ Electronic LSI
T35	= 310+ Electronic LSG
T36	= 310+ Electronic LSIG
T38	= 310+ Electronic LSI with Maintenance Mode
T39	= 310+ Electronic LSIG with Maintenance Mode

Features	
Blank	= No feature
B20	= High load alarm
B21	= Ground fault alarm, with trip
B22	= Ground fault alarm, no trip
ZG	= Zone selective interlocking

Terminals
W = No terminals

310+ Electronic Trip Unit ①

MES 3 800 ALSIG B21

Trip Unit Type
MES

Number of Poles
3 = Three-pole

Amperes
800

Trip Unit	
LS	= 310+ Electronic LS
LSI	= 310+ Electronic LSI
LSG	= 310+ Electronic LSG
LSIG	= 310+ Electronic LSIG
ALSI	= 310+ Electronic LSI with Maintenance Mode
ALSIG	= 310+ Electronic LSIG with Maintenance Mode

Features	
Blank	= No feature
B20	= High load alarm
B21	= Ground fault alarm, with trip
B22	= Ground fault alarm, no trip
ZG	= Zone selective interlocking

Note

① Frames are the same for thermal-magnetic or 310+ electronic trip units, e.g., **MDL3800F**, **HMDL3800F**, etc.

Product Selection

Types MDL and HMDL Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units—Two-Pole

	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac		High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac		Thermal-Magnetic Trip Unit Only For Use with Standard or High or Ultra High Interrupting Frames Magnetic Trip Range is 5–10 Up Through 600 A; 4–8 on 700 and 800 A x Continuous Ampere Rating	Standard Terminals Only [1] See Page V4-T2-217 for Optional Terminals
Maximum Continuous Ampere Rating at 40 °C	Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Frame Only Catalog Number	Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Frame Only Catalog Number	Catalog Number	Catalog Number
300	**MDL2300**	**MDL2800F**	**HMDL2300**	**HMDL2800F**	**MT2300T**	**TA700MA1**
350	**MDL2350**		**HMDL2350**		**MT2350T**	**TA700MA1**
400	**MDL2400**		**HMDL2400**		**MT2400T**	**TA700MA1**
450	**MDL2450**		**HMDL2450**		**MT2450T**	**TA700MA1**
500	**MDL2500**		**HMDL2500**		**MT2500T**	**TA700MA1**
600	**MDL2600**		**HMDL2600**		**MT2600T**	**TA700MA1**
700	**MDL2700**		**HMDL2700**		**MT2700T**	**TA700MA1**
800	**MDL2800**		**HMDL2800**		**MT2800T**	**TA800MA2**

Types MDL and HMDL Thermal-Magnetic Circuit Breakers with Interchangeable Trip Units—Three-Pole

	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac		High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac		Thermal-Magnetic Trip Unit Only For Use with Standard or High or Ultra High Interrupting Frames Magnetic Trip Range is 5–10 Up Through 600 A; 4–8 on 700 and 800 A x Continuous Ampere Rating	Standard Terminals Only [1] See Page V4-T2-217 for Optional Terminals
Maximum Continuous Ampere Rating at 40 °C	Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Frame Only Catalog Number	Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Frame Only Catalog Number	Catalog Number	Catalog Number
300	**MDL3300**	**MDL3800F**	**HMDL3300**	**HMDL3800F**	**MT3300T**	**TA700MA1**
350	**MDL3350**		**HMDL3350**		**MT3400T**	**TA700MA1**
400	**MDL3400**		**HMDL3400**		**MT3400T**	**TA700MA1**
450	**MDL3450**		**HMDL3450**		**MT3450T**	**TA700MA1**
500	**MDL3500**		**HMDL3500**		**MT3500T**	**TA700MA1**
600	**MDL3600**		**HMDL3600**		**MT3600T**	**TA700MA1**
700	**MDL3700**		**HMDL3700**		**MT3700T**	**TA700MA1**
800	**MDL3800**		**HMDL3800**		**MT3800T**	**TA800MA2**

Note

[1] Two terminals are required per pole.

Types MDLB and HMDLB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units—Two-Pole ①

Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Standard Terminals Only ② See Page V4-T2-217 for Optional Terminals Catalog Number
300	**MDLB2300**	**HMDLB2300**	**TA700MA1**
350	**MDLB2350**	**HMDLB2350**	**TA700MA1**
400	**MDLB2400**	**HMDLB2400**	**TA700MA1**
450	**MDLB2450**	**HMDLB2450**	**TA700MA1**
500	**MDLB2500**	**HMDLB2500**	**TA700MA1**
600	**MDLB2600**	**HMDLB2600**	**TA700MA1**
700	**MDLB2700**	**HMDLB2700**	**TA700MA1**
800	**MDLB2800**	**HMDLB2800**	**TA800MA2**

Types MDLB and HMDLB Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units—Three-Pole ①

Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Factory Assembled Circuit Consisting of Frame, Trip Unit and Terminals Catalog Number	Standard Terminals Only ② See Page V4-T2-217 for Optional Terminals Catalog Number
300	**MDLB3300**	**HMDLB3300**	**TA700MA1**
350	**MDLB3350**	**HMDLB3350**	**TA700MA1**
400	**MDLB3400**	**HMDLB3400**	**TA700MA1**
450	**MDLB3450**	**HMDLB3450**	**TA700MA1**
500	**MDLB3500**	**HMDLB3500**	**TA700MA1**
600	**MDLB3600**	**HMDLB3600**	**TA700MA1**
700	**MDLB3700**	**HMDLB3700**	**TA700MA1**
800	**MDLB3800**	**HMDLB3800**	**TA800MA2**

Notes

① Factory sealed for reverse feed application.

② Two terminals are required per pole.

Types MDL and HMDL Electronic Circuit Breakers with Interchangeable Trip Units

Order as Individual Components: breaker frame, trip unit and terminals.
See 310+ adjustability specifications on **Page V4-T2-220**.

Types MDL and HMDL Electronic Circuit Breakers with Interchangeable 310+ Trip Units—Three-Pole

	Circuit Breaker Frame Only		Digitrip RMS 310+ Trip Unit Only ①					
			Standard LS	Optional LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac Catalog Number	Adjustable Short Time Pickup with I^2t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
800	**MDL3800F**	**HMDL3800F**	**MES3800LS**	**MES3800LSI**	**MES3800LSG**	**MES3800LSIG**	**LGFCT600**	See **Page V4-T2-218**

Types MDLB and HMDLB Electronic Circuit Breakers with Non-Interchangeable 310+ Trip Units ④

	Factory-Assembled Circuit Breaker Consisting of Frame and Trip Unit Less Terminals				
	LS	LSI	LSG	LSIG	
Maximum Continuous Ampere Rating at 40 °C	Adjustable Short Time Pickup with I^2t Short Delay Ramp Catalog Number	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac					
800	**MDLB3800FT33W**	**MDLB3800FT32W**	**MDLB3800FT35W**	**MDLB3800FT36W**	**LGFCT600**
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
800	**HMDLB3800FT33W**	**HMDLB3800FT32W**	**HMDLB3800FT35W**	**HMDLB3800FT36W**	**LGFCT600**

100% Rated Types CMDL and CHMDL Electronic Circuit Breakers with Interchangeable Trip Units

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at the 75 °C ampacity. All 100% rated circuit breakers have electronic trip units. Order as individual components: breaker frame, trip unit and terminals. See 310+ adjustability specifications on **Page V4-T2-220**.

100% Rated Types CMDL and CHMDL Electronic Circuit Breakers with Interchangeable 310+ Trip Units—Three-Pole

	Circuit Breaker Frame Only		Digitrip RMS 310+ Trip Unit Only ①					
			Standard LS	Options LSI	LSG	LSIG		
Maximum Continuous Ampere Rating at 40 °C	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac Catalog Number	High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac	Adjustable Short Time Pickup with I^2t Short Delay Ramp	Independently Adjustable Short Time Pickup and Delay	Adjustable Short Time Pickup with I^2t Short Delay and Ground Fault Protection	Independently Adjustable Short Time Pickup and Ground Fault Protection	Neutral CT for LSG and LSIG ②③ Catalog Number	Terminal Information
800	**CMDL3800F**	**CHMDL3800F**	**MES3800LS**	**MES3800LSI**	**MES3800LSG**	**MES3800LSIG**	**LGFCT600**	See **Page V4-T2-218**

Notes

① For AC use only.
② Required for four-wire systems if neutral protection is desired.
③ Included with LSG and LSIG trip units or breakers.
④ Factory sealed, suitable for reverse feed application. CMDLB and CHMDLB are also available.

Molded Case Switches

Eaton's molded case switches are used as compact switches in applications requiring high current switching capabilities. Molded case switches are constructed of circuit breaker components and are of the high instantaneous automatic type. Molded case switches are listed in accordance with Underwriters Laboratories Standard UL 489.

Molded Case Switches

Maximum Continuous Ampere Rating at 40 °C	600 Vac Maximum, 250 Vdc Circuit Breaker Only without Line and Load Terminals Catalog Number
Two-Pole	
800	**MDL2800WK**
	MDLB2800WK ①
	HMDL2800WK
Three-Pole	
800	**MDL3800WK**
	MDLB3800WK ①
	HMDL3800WK

Notes

① MDLB and HMDLB are suitable for reverse feed applications.

Molded case switch may trip above 6000 amperes.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

M-Frame circuit breakers use Cu/Al terminals as standard. When optional copper or Cu/Al terminals are required, order by catalog number. Specify if factory installation is required.



TA700MA1



TA800MA2



TA801MA

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/No. Conductors	Terminal Catalog Number	Terminals with Control Wire Termination Catalog Number
Standard Cu/Al Pressure Terminals					
700	Aluminum	Cu/Al	1–500 kcmil (2)	**TA700MA1**	**TA700MA1CWT**
800 std.	Aluminum	Cu/Al	3/0–400 kcmil (3)	**TA800MA2**	**TA800MA2CWT**
800	Aluminum	Cu/Al	500–750 kcmil (2)	**TA801MA**	**TA801MACWT**
Optional Copper and Cu/Al Pressure Type Terminals					
600	Copper	Cu	2/0–500 kcmil (2)	**T600MA1**	—
800	Copper	Cu	3/0–300 kcmil (3)	**T800MA1**	—

Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

MD Frame Accessories

Description	Reference Page	Two-Pole ① Left	Two-Pole ① Right	Three-Pole Left	Three-Pole Center	Three-Pole Right
Internal Accessories (Only One Internal Accessory Per Pole)						
Alarm lockout (Make/Break)	**V4-T2-276**	■	■	■		■
Alarm lockout (2Make/2Break)	**V4-T2-276**	■	■	■		■
Auxiliary switch (1A, 1B)	**V4-T2-278**	■	■	■		■
Auxiliary switch (2A, 2B)	**V4-T2-278**	■	■	■		■
Auxiliary switch (3A, 3B)	**V4-T2-278**	■	■	■		■
Auxiliary switch (1A, 1B) and alarm switch combination	**V4-T2-280**	■	■	■		■
Auxiliary switch (2A, 2B) and alarm switch combination	**V4-T2-280**	■	■	■		■
Shunt trip—standard ②	**V4-T2-283**	■	■	■		■
Shunt trip—low energy ②	**V4-T2-285**	■	■	■		■
Undervoltage release mechanism ②	**V4-T2-291**	■	■	■		■
External Accessories						
Rear fed terminals	**V4-T2-312**	●	●	●	●	●
Base mounting hardware	**V4-T2-313**				●	
Terminal shields	**V4-T2-315**				●	
Interphase barriers	**V4-T2-315**				●	
Non-padlockable handle block	**V4-T2-316**				■	
Padlockable handle lock hasp	**V4-T2-317**	❑		❑		❑
Key interlock kit	**V4-T2-318**	❑		❑		❑
Sliding bar interlock—requires two breakers	**V4-T2-319**	●	●	●	●	●
Walking beam interlock—requires two breakers	**V4-T2-319**	●	●	●	●	●
Electrical (motor) operator	**V4-T2-320**	●	●	●	●	●
Plug-in adapters	**V4-T2-322**	●	●	●	●	●
Rear connecting studs	**V4-T2-323**	●	●	●	●	●
Panelboard connecting straps	**V4-T2-324**	●	●	●	●	●
Handle mechanisms	**V4-T2-427**	●	●	●	●	●
Handle extension	**V4-T2-442**	●	●	●	●	●
Solid-state (electronic) portable test kit	**V4-T2-326**	●	●	●	●	●
Modifications (Refer to Eaton)						
Special calibration	—	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●

Legend

■ Applicable in indicated pole position

❑ May be mounted on left or right pole—not both

● Accessory available/modification available

Notes

① Two-pole breaker supplied in three-pole frame. Current carrying parts omitted from center pole.

② Shunt trip and UVR cannot be mounted in right poles on MES trip units.

310+ Electronic Trip Unit Accessories

Description	Catalog Number
Electronic portable test kit	**MTST230V** ①
Trip unit tamper protection wire seal	**5108A03H01**
External neutral sensor	**LGFCT600** ②
Breaker-mount cause-of-trip indication	**TRIP-LED**
Breaker-mount ammeter module	**DIGIVIEW**
Remote-mount ammeter module	**DIGIVIEWR06** ③

Technical Data and Specifications

UL 489/CSA Interrupting Capacity Ratings ④

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	480	600	Volts DC ⑤⑥ 250
MDL, MDLB	2, 3	65	50	25	22
CMDL	2, 3	65	50	25	—
HMDL, HMDLB	2, 3	100	65	35	25
CHMDL	2, 3	100	65	35	—

IEC 947-2 Interrupting Capacity Ratings ④

Circuit Breaker Type	Number of Poles	Interrupting Capacity rms (kA Symmetrical Amperes) $I_{cu} = I_{cs}$ Volts AC (50/60 Hz) 240	415	690	Volts DC ⑤⑥ 250
MDL, MDLB	2, 3	65/65	50/50	20/10	20/10
CMDL	2, 3	65/65	50/50	20/10	—
HMDL, HMDLB	2, 3	100/100	70/50	25/13	20/10
CHMDL	2, 3	100/100	70/50	25/13	—

Notes

① MTST230V applies to 100–230 Vac.
② Included with all LD LSG and LSIG trip units and breakers.
③ Includes 6 ft cable for remote mounting; NEMA 3R rated.
④ Utilization Category A circuit breakers.
⑤ Two-pole or two poles of three-pole circuit breaker. Thermal-magnetic trip units only, MDL, HMDL breakers with electronic trip unit are not DC rated.
⑥ Time constant is 3 milliseconds minimum at 10 kA and 8 milliseconds at 22 kA.

310+ Specifications

Description	Specification
Trip Unit Type	Digitrip RMS 310+
Breaker Type	
Frame designation	MDL
Frames available	800 A
Continuous current range (A)	320–800 A
Ground fault pickup (A)	160–800 A
Interrupting capacities at 480 Vac (kAIC)	50, 65
100% rated	Yes
Protection	
Ordering options	LS, LSI, LSG, LSIG, ALSI, ALSIG
Arcflash Reduction Maintenance System (or Maintenance Mode)	Remote enabled on ALSI, ALSIG
Interchangeable trip unit	Yes
High load alarm (suffix B20) ①	Yes
Ground fault alarm with trip (suffix B21) ①	LSG, LSIG, ALSIG
Ground fault alarm, no trip (suffix B22) ①	LSG, LSIG, ALSIG
Zone selective interlocking (suffix ZG)	LSI, LSIG, ALSI, ALSIG
Cause of trip indication	Yes (via TRIP-LED or DIGIVIEW)
Thru-cover accessories	No

310+ Adjustability Specifications

Description		MDL Frame Specification
310+ settings		800 A
I_r = continuous current or long delay pickup (amperes) (All 310+)	I_r	
	A	320
	B	400
	C	450
	D	500
	E	600
	F	630
	G	700
	H (= I_n)	800
t_r = long delay time (seconds) (All 310+)	2	2
	4	4
	7	7
	10	10
	12	12
	15	15
	20	20
	24	24
I_{sd} (x I_r) = short delay pickup (All 310+)	Position 1	2x
	Position 2	3x
	Position 3	4x
	Position 4	5x
	Position 5	6x
	Position 6	7x
	Position 7	8x
	Position 8	8x
	Position 9	8x
t_{sd} = short delay time I^2t (milliseconds) (LS and LSG)	Fixed	67 @10x
t_{sd} = short delay time flat (milliseconds) (LSI, LSIG, ALSI, ALSIG)	Position 1	Inst
	Position 2	120
	Position 3	300
I_g (x I_n) = ground fault pickup (amperes) (310+ w/ ground fault)	Position 1	160
	Position 2	240
	Position 3	320
	Position 4	480
	Position 5	640
	Position 6	800
t_g = ground fault delay time (milliseconds) (LSG, LSIG, ALSIG)	Position 1	Inst
	Position 2	120
	Position 3	300
Independently adjustable Instantaneous (Ii) setting	②	
Maintenance Mode pickup (2.5 x I_n) (amperes) (310+ with Maintenance Mode—ALSI and ALSIG)	Fixed	2000

Notes

① B2x suffixes cannot be combined with B2x suffixes.

② Not available for MDL. Independently adjustable Ii setting available in LG, NG, and RG ALSI and ALSIG trip units.

Dimensions and Weights

Dimensions in Inches (mm)

MD Frame

Number of Poles	Width	Height	Depth
2, 3	8.25 (209.6)	16.00 (406.4)	4.06 (103.1)

MDL-Frame, Two- and Three-Pole

Drilling Plan



Front View



Side View



Approximate Shipping Weight, Lbs (kg)

MD Frame

	Complete Breaker		Frame Only		Trip Unit ①	
Breaker Type	Two-Pole	Three-Pole	Two-Pole	Three-Pole	Two-Pole	Three-Pole
MDL, HMDL (T/M T.U.)	26.5 (12.0)	29.0 (13.2)	24.5 (11.1)	26.0 (11.8)	2.5 (1.1)	3.0 (1.4)
MDL, HMDL (Elec. T.U.)	—	30.0 (13.6)	—	26.0 (11.8)	—	4.0 (1.8)

Note

① Thermal-magnetic only.

Typical N-Frame Breaker

2

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	
Catalog Number Selection	**V4-T2-223**
Product Selection	**V4-T2-224**
Accessories	**V4-T2-232**
Technical Data and Specifications	**V4-T2-233**
Dimensions and Weights	**V4-T2-236**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

N-Frame (400–1200 Amperes)

Product Description

- All Eaton N-Frame circuit breakers are suitable for reverse feed use
- All N-Frame circuit breakers are HACR rated

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

Circuit Breaker/Frame



Product Selection

2

Digitrip OPTIM Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plugs

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)			Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac					
800	**ND3800T52W**	**ND3800T56W**	**ND3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200	**ND312T52W**	**ND312T56W**	**ND312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
800	**HND3800T52W**	**HND3800T56W**	**HND3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200	**HND312T52W**	**HND312T56W**	**HND312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 550 Electronic Circuit Breakers with Interchangeable Rating Plugs, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Digitrip OPTIM Rating Plug Only Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac					
800	**NDC3800T52W**	**NDC3800T56W**	**NDC3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200	**NDC312T52W**	**NDC312T56W**	**NDC312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

Digitrip OPTIM 1050 Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L– Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ① S– Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I– Adjustable Instantaneous Pickup G– Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) A– Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response) OPTIM 1050 ②③		Digitrip OPTIM Rating Plug Only	
	LSIG	LSIA		Fixed Rating Plug
	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac				
800	**ND3800T106W**	**ND3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			500	**ORPN80A500**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**ND312T106W**	**ND312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
800	**HND3800T106W**	**HND3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			500	**ORPN80A500**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**HND312T106W**	**HND312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**
Three-Pole Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac				
800	**NDC3800T106W**	**NDC3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			500	**ORPN80A500**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**NDC312T106W**	**NDC312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch and one Form C bell (trip) alarm switch supplied with breaker as standard.
③ Factory sealed.

100% Rated Digitrip OPTIM Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit), rating plug, terminals.

100% Rated Digitrip OPTIM 550 Circuit Breakers with Interchangeable Rating Plugs

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)

Digitrip OPTIM Rating Plug Only

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac					
800	**CND3800T52W**	**CND3800T56W**	**CND3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200 ③	**CND312T52W**	**CND312T56W**	**CND312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac					
800	**CHND3800T52W**	**CHND3800T56W**	**CHND3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200 ③	**CHND312T52W**	**CHND312T56W**	**CHND312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.
③ Includes conductor extension kit, which increases breaker length 3.75 on each end. Terminal ordered separate.

100% Rated Digitrip OPTIM 550 Circuit Breakers with Interchangeable Rating Plugs, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)

Maximum Continuous Ampere Rating at 40 °C	OPTIM 550 ② LSI Catalog Number	LSIG Catalog Number	LSIA Catalog Number	Digitrip OPTIM Rating Plug Only Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac					
800	**CNDC3800T52W**	**CNDC3800T56W**	**CNDC3800T57W**	400	**ORPN80A400**
				450	**ORPN80A450**
				500	**ORPN80A500**
				550	**ORPN80A550**
				600	**ORPN80A600**
				700	**ORPN80A700**
				800	**ORPN80A800**
1200 ③	**CNDC312T52W**	**CNDC312T56W**	**CNDC312T57W**	600	**ORPN12A600**
				700	**ORPN12A700**
				800	**ORPN12A800**
				1000	**ORPN12A100**
				1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.

② Zone interlocking, PowerNet, or both features can be added at the factory by adding suffixes **ZG**, **PN** or **ZGP** respectively to above catalog number.

③ Includes conductor extension kit, which increases breaker length 3.75 on each end. Terminal ordered separate.

100% Rated Digitrip OPTIM 1050 Circuit Breakers with Interchangeable Rating Plugs

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)

Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Digitrip OPTIM Rating Plug Only Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac				
800	**CND3800T106W**	**CND3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			500	**ORPN80A500**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**CND312T106W**	**CND312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**
Three-Pole High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
800	**CHND3800T106W**	**CHND3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**CHND312T106W**	**CHND312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch one Form C bell (trip) alarm switch supplied with breaker as standard.
③ Factory sealed.

100% Rated Digitrip OPTIM 1050 Circuit Breakers with Interchangeable Rating Plugs, continued

Circuit Breaker Frame Only

L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time (I^2t or I^4t Response) ①
S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response)
I – Adjustable Instantaneous Pickup
G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)
A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)

Maximum Continuous Ampere Rating at 40 °C	OPTIM 1050 ②③ LSIG Catalog Number	LSIA Catalog Number	Digitrip OPTIM Rating Plug Only Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Ultra High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac				
800	**CNDC3800T106W**	**CNDC3800T107W**	400	**ORPN80A400**
			450	**ORPN80A450**
			500	**ORPN80A500**
			550	**ORPN80A550**
			600	**ORPN80A600**
			700	**ORPN80A700**
			800	**ORPN80A800**
1200	**CNDC312T106W** ④	**CNDC312T107W**	600	**ORPN12A600**
			700	**ORPN12A700**
			800	**ORPN12A800**
			1000	**ORPN12A100**
			1200	**ORPN12A120**

Type ND Molded Case Switches

Type ND High Instantaneous (K)

Continuous Ampere Rating at 40 °C	Three-Pole Catalog Number	Four-Pole ⑤ Catalog Number
800	**ND3800WK**	**ND4800WK**
	HND3800WK	**HND4800WK**
1200	**ND312WK**	**ND412WK**
	HND312WK	**HND412WK**

Notes

① Long delay I^4t response selection limits short delay time to flat response.
② One Form C auxiliary switch one Form C bell (trip) alarm switch supplied with breaker as standard.
③ Factory sealed.
④ Includes conductor extension kit, which increases breaker length 3.75 on each end. Terminal ordered separate.
⑤ Neutral is in right pole.

Molded case switch will trip above 14,000 amperes.

For UL listed, series tested molded case switch application data, refer to Eaton.

Accessories Selection Guide and Ordering Information

Line and Load Terminals—Ordering Information

N-Frame circuit breakers use Cu/Al terminals as standard. When optional copper or Cu/Al terminals are required, order by catalog number. Specify if factory installation is required.


TA700NB1


TA1000NB1


TA1200NB1


TA1201NB1


T700NB1


T1000NB1

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range/ No. Conductors	Metric Wire Range mm^2	Catalog Number
Standard Cu/Al Pressure Terminals					
700	Aluminum	Cu/Al	1–500 kcmil (2)	50–240	**TA700NB1**
1000	Aluminum	Cu/Al	3/0–400 kcmil (3)	95–185	**TA1000NB1** ①
1200	Aluminum	Cu/Al	4/0–500 kcmil (4)	120–240	**TA1200NB1** ①
1200	Aluminum	Cu/Al	500–750 kcmil (3)	300–400	**TA1201NB1** ②
Optional Copper and Cu/Al Pressure Type Terminals					
700	Copper	Cu	2/0–500 kcmil (2)	70–240	**T700NB1**
1000	Copper	Cu	3/0–500 kcmil (3)	95–240	**T1000NB1**
1200	Copper	Cu	3/0–400 kcmil (4)	95–185	**T1200NB3**

Notes

① Terminal rating is AL9CU.
② Terminal rating is AL7CU.

Accessories

2

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

ND Frame Accessories

Description	Reference Page	Three-Pole Left	Center	Right	Four-Pole Left	Center	Right	Neutral
Internal Accessories (Only One Internal Accessory Per Pole) ①								
Alarm lockout (Make/Break)	**V4-T2-276**	■		■	■		■	
Alarm lockout (2Make/2Break)	**V4-T2-276**	■		■	■		■	
Auxiliary switch (1A, 1B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (2A, 2B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (3A, 3B)	**V4-T2-278**	■		■	■		■	
Auxiliary switch (1A, 1B) and alarm switch combination	**V4-T2-280**	■		■	■		■	
Auxiliary switch (2A, 2B) and alarm switch combination	**V4-T2-280**	■		■	■		■	
Shunt trip—standard	**V4-T2-284**	■			■			
Shunt trip—low energy	**V4-T2-285**	■			■			
Undervoltage release mechanism	**V4-T2-292**	■			■			
Eaton PowerNet communications kit (OPTIM 550)	**V4-T2-293**			■				
External Accessories								
Base mounting hardware	**V4-T2-313**	●	●	●	●	●	●	●
Interphase barriers	**V4-T2-315**	●	●	●	●	●	●	●
Terminal shield	**V4-T2-315**	■	■	■				
Non-padlockable handle block	**V4-T2-316**		■			■		
Padlockable handle lock hasp	**V4-T2-317**	❑		❑	❑		❑	
Key interlock kit	**V4-T2-318**	❑		❑	❑		❑	
Sliding bar interlock—requires two breakers	**V4-T2-319**	●	●	●				
Walking beam interlock—requires two breakers	**V4-T2-319**	●	●	●	●	●	●	●
Electrical (motor) operator	**V4-T2-321**	●	●	●	●	●	●	●
Plug-in adapters	**V4-T2-322**	●	●	●	●	●	●	●
Rear connecting studs	**V4-T2-323**	●	●	●	●	●	●	●
Panelboard connecting straps	**V4-T2-324**	●	●	●	●	●	●	●
Handle mechanisms	**V4-T2-427**	●	●	●	●	●	●	●
Handle extension	**V4-T2-442**	●	●	●	●	●	●	●
Solid-state (electronic) portable test kit	**V4-T2-327**	●	●	●	●	●	●	●
OPTIM System Components Three Poles								
Ground fault alarm unit	**V4-T2-326**							
Potential transformer module	**V4-T2-326**							
Breaker interface module (BIM)	**V4-T2-327**							
Digitrip OPTIMizer	**V4-T2-327**							
Auxiliary power module	**V4-T2-327**							
Modifications (Refer to Eaton)								
Special calibration	—	●	●	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position

❑ May be mounted on left or right pole—not both

● Accessory available/modification available

Note

① OPTIM 550 and 1050 are factory sealed and do not have the right pole available for accessories.

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600
ND	2, 3, 4	65	—	50	25
CND ②	2, 3, 4	65	—	50	25
HND	2, 3, 4	100	—	65	35
CHND ②	2, 3, 4	100	—	65	35
NDC	2, 3, 4	200	—	100	65
CNDC ②	2, 3, 4	200	—	100	65
NDU ③	3	300 ④	—	150	75 ⑤

IEC 947-2 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	415	690
ND				
I_{cu}	2, 3, 4	85	50	20
I_{cs}	2, 3, 4	85	50	10
CND ②				
I_{cu}	2, 3, 4	85	50	20
I_{cs}	2, 3, 4	85	50	10
HND				
I_{cu}	2, 3, 4	100	70	25
I_{cs}	2, 3, 4	100	50	13
CHND ②				
I_{cu}	2, 3, 4	100	70	25
I_{cs}	2, 3, 4	100	50	13
NDC				
I_{cu}	2, 3, 4	200	100	35
I_{cs}	2, 3, 4	100	50	18
CNDC ②				
I_{cu}	2, 3, 4	200	100	35
I_{cs}	2, 3, 4	100	50	18

Notes

① Utilization Category A circuit breakers.
② 100% rated breakers.
③ 800 amperes maximum rating.
④ Successfully tested at 300 kAIC, although UL recognizes maximum of 200 kAIC at 240 Vac.
⑤ Successfully tested at 75 kAIC, although UL recognizes maximum of 65 kAIC at 600 Vac.

N-Frame Digitrip

Trip Unit Type	Digitrip OPTIM 550	Digitrip OPTIM 1050
rms sensing	Yes	Yes
Breaker Type		
Frame	N	N
Ampere range	400–1200 A	400–1200 A
Interrupting rating at 480 volts	50, 65, 100 (kA)	50, 65, 100 (kA)
Protection		
Ordering options	LSI, LSIG, LSI(A)	LSI(A), LISG
Fixed rated plug (I_n)	Yes	Yes
Overtemperature trip	Yes	Yes
Long Delay Protection (L)		
Adjustable rating plug (I_n)	No	No
Long delay pickup	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)
Long delay time I^2t	2–24 seconds	2–24 seconds
Long delay time I^4t	1–5 seconds	1–5 seconds
Long delay thermal memory	Yes	Yes
High load alarm	No	0.5–1.0 x I_r
Short Delay Protection (S)		
Short delay pickup	150–800% x (I_r)	150–800% x (I_r)
Short delay time I^2t	100–500 ms	100–500 ms
Short delay time flat	100–500 ms	100–500 ms
Short delay time zone selective interlocking	Yes	Yes
Instantaneous Protection (I)		
Instantaneous pickup	200–800% x (I_n)	200–800% x (I_n)
Discriminator	Yes	Yes
Instantaneous override	Yes	Yes
Ground Fault Protection (G)		
Ground fault alarm	20–100% x (I_s)	20–100% x (I_s)
Ground fault pickup	20–100% x (I_s)	20–100% x (I_s)
Ground fault delay I^2t	100–500 ms	100–500 ms
Ground fault delay flat	100–500 ms	100–500 ms
Ground fault zone selective interlocking	Yes ①	Yes
Ground fault thermal memory	Yes	Yes
System Diagnostics		
Status LEDs	Yes	Yes
Cause of trip LEDs	Yes	Yes
Magnitude of trip information	Yes	Yes
Remote signal contact—ground alarm	Yes ①	Yes
Local auxiliary and bell alarm contact	Optional	Included

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting

Note

① Zone interlock kit.

N-Frame Digitrip, continued

Trip Unit Type	Digitrip OPTIM 550	Digitrip OPTIM 1050
System Monitoring		
Digital display	Yes ①	Yes ①
Current	Yes	Yes
Power and energy	No	Yes
Power quality—harmonics	No	Yes
Power factor	No	Yes
Communications		
Eaton PowerNet	No ②	Yes
Testing		
Testing method	OPTIMizer, BIM, PowerNet	OPTIMizer, BIM, PowerNet

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting

Notes

① By OPTIMizer/BIM.
② Eaton's PowerNet kit.

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

ND Frame

Number of Poles	Width	Height	Depth
2, 3	8.25 (209.6)	16.00 (406.4)	5.50 (139.7)
4	11.13 (282.6)	16.00 (406.4)	5.50 (139.7)

ND-Frame, Two- and Three-Pole

Front Cover Cutout



Front View



Side View



Approximate Shipping Weight in Lbs (kg)

ND Frame

	Complete Breaker		
Breaker Type	Two-Pole	Three-Pole	Four-Pole
ND, HND, NDC, NDU	37 (16.8)	45 (20.4)	58 (26.3)

Typical R-Frame Breaker

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	
Catalog Number Selection	**V4-T2-238**
Product Selection	**V4-T2-239**
Accessories	**V4-T2-251**
Technical Data and Specifications	**V4-T2-252**
Dimensions and Weights	**V4-T2-255**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

R-Frame (800–2500 Amperes)

Product Description

- Eaton R-Frame circuit breakers are available as frame (which includes trip unit), rating plug and terminals
- All R-Frame circuit breakers are suitable for reverse feed use

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers or trip units.

2

Circuit Breaker/Frame

RD 3 16 T53 W

Circuit Breaker/ Frame Type
RD
RDC
CRD ②
CRDC ②

Number of Poles
3 = Three-pole
4 = Four-pole

Circuit Breaker/Frame Ampere Rating
16 = 1600 amperes
20 = 2000 amperes
25 = 2500 amperes

Trip Type ①	
T53	= Digitrip RMS 510 LS
T65	= Digitrip RMS 610 LSG
T86	= Digitrip RMS 810 LSIG
T96	= Digitrip RMS 910 LSIG
T106	= Digitrip OPTIM 1050 LSIG
T107	= Digitrip OPTIM 1050 LSIA

Suffix	
W	= Without terminals
P	= 100% protected neutral pole
R	= Ground fault remote (310 only)
K	= Molded case switch

Notes

① For complete list of available trip types, refer to **Pages V4-T2-239** to **V4-T2-248**.

② No four-pole for CRD and CRDC.

Product Selection

Digitrip RMS 510 Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

Digitrip RMS 510 Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number						Digitrip Rating Plug Only Rated Current (I_n)	Fixed Rating Plug Catalog Number
	LS	LSI	LIG	LSG	LSIG			
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**RD316T51W**	**RD316T53W**	**RD316T52W**	**RD316T54W**	**RD316T55W**	**RD316T56W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RD320T51W**	**RD320T53W**	**RD320T52W**	**RD320T54W**	**RD320T55W**	**RD320T56W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RD325T51W**	**RD325T53W**	**RD325T52W**	**RD325T54W**	**RD325T55W**	**RD325T56W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**RDC316T51W**	**RDC316T53W**	**RDC316T52W**	**RDC316T54W**	**RDC316T55W**	**RDC316T56W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RDC320T51W**	**RDC320T53W**	**RDC320T52W**	**RDC320T54W**	**RDC320T55W**	**RDC320T56W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RDC325T51W**	**RDC325T53W**	**RDC325T52W**	**RDC325T54W**	**RDC325T55W**	**RDC325T56W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**

100% Rated Digitrip RMS 510 Circuit Breakers

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at 75 °C ampacity. Order as individual components: breaker frame (which includes trip unit) and rating plug.

100% Rated Digitrip RMS 510 Circuit Breakers

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number						Digitrip Rating Plug Only Rated Current (I_n)	Fixed Rating Plug Catalog Number
		LS	LSI	LIG	LSG	LSIG		
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**CRD316T51W**	**CRD316T53W**	**CRD316T52W**	**CRD316T54W**	**CRD316T55W**	**CRD316T56W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRD320T51W**	**CRD320T53W**	**CRD320T52W**	**CRD320T54W**	**CRD320T55W**	**CRD320T56W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	—	**CRDC316T53W**	**CRDC316T52W**	**CRDC316T54W**	**CRDC316T55W**	**CRDC316T56W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRDC320T51W**	**CRDC320T53W**	**CRDC320T52W**	**CRDC320T54W**	**CRDC320T55W**	**CRDC320T56W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**

Note

① Includes B2016RDL rear connectors.

Digitrip RMS 610 Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

Digitrip RMS 610 Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number						Digitrip Rating Plug Only Rated Current (I_n)	 Fixed Rating Plug Catalog Number
	LS	LSI	LIG	LSG	LSIG			
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**RD316T61W**	**RD316T63W**	**RD316T62W**	**RD316T64W**	**RD316T65W**	**RD316T66W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RD320T61W**	**RD320T63W**	**RD320T62W**	**RD320T64W**	**RD320T65W**	**RD320T66W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RD325T61W**	**RD325T63W**	**RD325T62W**	**RD325T64W**	**RD325T65W**	**RD325T66W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**RDC316T61W**	**RDC316T63W**	**RDC316T62W**	**RDC316T64W**	**RDC316T65W**	**RDC316T66W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RDC320T61W**	**RDC320T63W**	**RDC320T62W**	**RDC320T64W**	**RDC320T65W**	**RDC320T66W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RDC325T61W**	**RDC325T63W**	**RDC325T62W**	**RDC325T64W**	**RDC325T65W**	**RDC325T66W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**

100% Rated Digitrip RMS 610 Circuit Breakers

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at 75 °C ampacity. Order as individual components: breaker frame (which includes trip unit) and rating plug.

100% Rated Digitrip RMS 610 Circuit Breakers

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number	LS	LSI	LIG	LSG	LSIG	Digitrip Rating Plug Only Rated Current (I_n)	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**CRD316T61W**	**CRD316T63W**	**CRD316T62W**	**CRD316T64W**	**CRD316T65W**	**CRD316T66W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRD320T61W**	**CRD320T63W**	**CRD320T62W**	**CRD320T64W**	**CRD320T65W**	**CRD320T66W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**CRDC316T61W**	**CRDC316T63W**	**CRDC316T62W**	**CRDC316T64W**	**CRDC316T65W**	**CRDC316T66W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRDC320T61W**	**CRDC320T63W**	**CRDC320T62W**	**CRDC320T64W**	**CRDC320T65W**	**CRDC320T66W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**

Note

① Includes B2016RDL rear connectors.

Digitrip RMS 810 Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

Digitrip RMS 810 Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number	LS	LSI	LIG	LSG	LSIG	Digitrip Rating Plug Only Rated Current (I_n)	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**RD316T81W**	**RD316T83W**	**RD316T82W**	**RD316T84W**	**RD316T85W**	**RD316T86W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RD320T81W**	**RD320T83W**	**RD320T82W**	**RD320T84W**	**RD320T85W**	**RD320T86W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RD325T81W**	**RD325T83W**	**RD325T82W**	**RD325T84W**	**RD325T85W**	**RD325T86W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**RDC316T81W**	**RDC316T83W**	**RDC316T82W**	**RDC316T84W**	**RDC316T85W**	**RDC316T86W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RDC320T81W**	**RDC320T83W**	**RDC320T82W**	**RDC320T84W**	**RDC320T85W**	**RDC320T86W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RDC325T81W**	**RDC325T83W**	**RDC325T82W**	**RDC325T84W**	**RDC325T85W**	**RDC325T86W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**

100% Rated Digitrip RMS 810 Circuit Breakers

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at 75 °C ampacity. Order as individual components: breaker frame (which includes trip unit) and rating plug.

100% Rated Digitrip RMS 810 Circuit Breakers

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)						Digitrip Rating Plug Only	
	LI	LS	LSI	LIG	LSG	LSIG	Rated Current (I_n)	Fixed Rating Plug
	Catalog Number							Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**CRD316T81W**	**CRD316T83W**	**CRD316T82W**	**CRD316T84W**	**CRD316T85W**	**CRD316T86W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRD320T81W**	**CRD320T83W**	**CRD320T82W**	**CRD320T84W**	**CRD320T85W**	**CRD320T86W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**CRDC316T81W**	**CRDC316T83W**	**CRDC316T82W**	**CRDC316T84W**	**CRDC316T85W**	**CRDC316T86W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRDC320T81W**	**CRDC320T83W**	**CRDC320T82W**	**CRDC320T84W**	**CRDC320T85W**	**CRDC320T86W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**

Note

① Includes B2016RDL rear connectors.

Digitrip RMS 910 Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

Digitrip RMS 910 Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) LI Catalog Number						Digitrip Rating Plug Only	
	LS	LSI	LIG	LSG	LSIG		Rated Current (I_n)	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**RD316T91W**	**RD316T93W**	**RD316T92W**	**RD316T94W**	**RD316T95W**	**RD316T96W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RD320T91W**	**RD320T93W**	**RD320T92W**	**RD320T94W**	**RD320T95W**	**RD320T96W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RD325T91W**	**RD325T93W**	**RD325T92W**	**RD325T94W**	**RD325T95W**	**RD325T96W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**RDC316T91W**	**RDC316T93W**	**RDC316T92W**	**RDC316T94W**	**RDC316T95W**	**RDC316T96W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000	**RDC320T91W**	**RDC320T93W**	**RDC320T92W**	**RDC320T94W**	**RDC320T95W**	**RDC320T96W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
2500	**RDC325T91W**	**RDC325T93W**	**RDC325T92W**	**RDC325T94W**	**RDC325T95W**	**RDC325T96W**	1600	**RP6R25A160**
							2000	**RP6R25A200**
							2500	**RP6R25A250**

100% Rated Digitrip RMS 910 Circuit Breakers

The NEC allows the breaker to be rated at 100% of its frame size in an assembly, provided that 90 °C wire is applied at 75 °C ampacity. Order as individual components: breaker frame (which includes trip unit) and rating plug.

100% Rated Digitrip RMS 910 Circuit Breakers

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response)						Digitrip Rating Plug Only	
	LI	LS	LSI	LIG	LSG	LSIG	Rated Current (I_n)	Fixed Rating Plug
	Catalog Number							Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac								
1600	**CRD316T91W**	**CRD316T93W**	**CRD316T92W**	**CRD316T94W**	**CRD316T95W**	**CRD316T96W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
							1600	**RP6R16A160**
2000 ①	**CRD320T91W**	**CRD320T93W**	**CRD320T92W**	**CRD320T94W**	**CRD320T95W**	**CRD320T96W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac								
1600	**CRDC316T91W**	**CRDC316T93W**	**CRDC316T92W**	**CRDC316T94W**	**CRDC316T95W**	**CRDC316T96W**	800	**RP6R16A080**
							1000	**RP6R16A100**
							1000	**RP6R16A100**
							1200	**RP6R16A120**
2000 ①	**CRDC320T91W**	**CRDC320T93W**	**CRDC320T92W**	**CRDC320T94W**	**CRDC320T95W**	**CRDC320T96W**	1000	**RP6R20A100**
							1200	**RP6R20A120**
							1600	**RP6R20A160**
							2000	**RP6R20A200**

Note

① Includes B2016RDL rear connectors.

Digitrip OPTIM Electronic Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

Digitrip OPTIM Electronic Circuit Breakers with Interchangeable Rating Plugs

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
	LSIA 1050	LSIG 1050		Fixed Rating Plug
	Catalog Number	Catalog Number	Ampere Rating	Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
1600	**RD316T107W**	**RD316T106W**	800	**ORPR16A080**
			1000	**ORPR16A100**
			1200	**ORPR16A120**
			1600	**ORPR16A160**
2000	**RD320T107W**	**RD320T106W**	1000	**ORPR20A100**
			1200	**ORPR20A120**
			1600	**ORPR20A160**
			2000	**ORPR20A200**
2500	**RD325T107W**	**RD325T106W**	1600	**ORPR25A160**
			2000	**ORPR25A200**
			2500	**ORPR25A250**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac				
1600	**RDC316T107W**	**RDC316T106W**	800	**ORPR16A080**
			1000	**ORPR16A100**
			1200	**ORPR16A120**
			1600	**ORPR16A160**
2000	**RDC320T107W**	**RDC320T106W**	1000	**ORPR20A100**
			1200	**ORPR20A120**
			1600	**ORPR20A160**
			2000	**ORPR20A200**
2500	**RDC325T107W**	**RDC325T106W**	1600	**ORPR25A160**
			2000	**ORPR25A200**
			2500	**ORPR25A250**

100% Rated 600 Volts AC Digitrip OPTIM Circuit Breakers with Interchangeable Rating Plugs

Order as individual components: breaker frame (which includes trip unit) and rating plug.

100% Rated 600 Volts AC Digitrip OPTIM Circuit Breakers with Interchangeable Rating Plugs

	Circuit Breaker Frame Only L – Adjustable Long Delay Pickup (I_r) with Adjustable Long Delay Time S – Adjustable Short Delay Pickup with Adjustable Short Delay Time (I^2t or Flat Response) I – Adjustable Instantaneous Pickup G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Time Delay (I^2t or Flat Response) A – Adjustable Ground Fault Alarm with Adjustable Ground Fault Time Delay (I^2t or Flat Response)		Digitrip OPTIM Rating Plug Only	
Maximum Continuous Ampere Rating at 40 °C	LSIA 1050 Catalog Number	LSIG 1050 Catalog Number	Ampere Rating	Fixed Rating Plug Catalog Number
Three-Pole Standard Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac				
1600	**CRD316T107W**	**CRD316T106W**	800	**ORPR16A080**
			1000	**ORPR16A100**
			1200	**ORPR16A120**
			1600	**ORPR16A160**
2000 ①	**CRD320T107W**	**CRD320T106W**	1000	**ORPR20A100**
			1200	**ORPR20A120**
			1600	**ORPR20A160**
			2000	**ORPR20A200**
Three-Pole High Interrupting Capacity 600 Vac Rated 100 kAIC at 480 Vac				
1600	**CRDC316T107W**	**CRDC316T106W**	800	**ORPR16A080**
			1000	**ORPR16A100**
			1200	**ORPR16A120**
			1600	**ORPR16A160**
2000 ①	**CRDC320T107W**	**CRDC320T106W**	1000	**ORPR20A100**
			1200	**ORPR20A120**
			1600	**ORPR20A160**
			2000	**ORPR20A200**

Molded Case Switches

Refer to Eaton for UL listed, series tested Molded Case Switch application data.

Type RD—High Instantaneous (K)

Continuous Ampere Rating at 40 °C	Complete without Terminals Three-Pole Catalog Number	 Four-Pole Catalog Number
1600	**RD316WK**	**RD416WK**
2000	**RD320WK**	**RD420WK**

Notes

① Includes B2016RDL rear connectors.

Molded case switch may trip above 17,500 amperes.

Accessories Selection Guide and Ordering Information

Line and Load Terminals

Line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. All terminals comply with Underwriters Laboratories Standards UL 486A and UL 486B and CSA C22.2 No. 65M. Unless otherwise specified, R-Frame circuit breaker line load terminals are shipped separately for field installation.

Ordering Information

R-Frame circuit breakers have Cu/Al terminals as standard and Cu only terminals as an option. Specify if factory installation is required.

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	Hardware	AWG/kcmil Wire Range/ No. Conductors	Metric Wire Range mm^2	Catalog Number
Wire Terminals						
1600	Aluminum	Cu/Al	English	500–1000 (4)	300–500	**TA1600RD**
1600	Copper	Cu	English	1–600 (4)	50–300	**T1600RD**
2000	Aluminum	Cu/Al	English	2–600 (6)	35–300	**TA2000RD** ①
Rear Connectors						
2000	Copper	—	English	—	—	**B2016RD**
2000	Copper	—	English	—	—	**B2016RDL** ②
2500	Copper	—	English	—	—	**B2500RD** ③

Notes

① Catalog Number includes bus connection, terminals and hardware for either line side or load side of three-pole breaker.

② For use with 100% rated 1600 A and 2000 A frame. Do not order separately unless for replacement purposes. Included in breaker carton when 100% rated device is ordered.

③ For use with 2500 A frame. Do not order separately unless for replacement purposes. Included in breaker carton when 2500 A breaker is ordered.

Mounting Hardware



TA2000RD



Accessories

Allowable Accessory Combinations

Different combinations of accessories can be supplied, depending on the types of accessories and the number of poles in the circuit breaker.

RD Frame Accessories

Description	Reference Page	Three-Pole Left	Three-Pole Center	Three-Pole Right	Four-Pole Left	Four-Pole Center	Four-Pole Right	Four-Pole Neu.
Internal Accessories ①								
Alarm lockout (Make/Break)	**V4-T2-276**			■			■	
Alarm lockout (2Make/2Break)	**V4-T2-276**			■			■	
Auxiliary switch (2A, 2B)	**V4-T2-276**			■			■	
Auxiliary switch (4A, 4B)	**V4-T2-276**			■			■	
Shunt trip—standard	**V4-T2-284**			■			■	
Shunt trip—low energy	**V4-T2-285**			■			■	
Undervoltage release mechanism	**V4-T2-292**			■			■	
Accessory terminal block ②	**V4-T2-293**			■				■
External Accessories								
Base mounting hardware	**V4-T2-313**							
Padlockable handle lock hasp	**V4-T2-316**		●			●		
Key interlock kit	**V4-T2-318**	■	■	■		■		
Walking beam interlock	**V4-T2-319**							
Electrical (motor) operator	**V4-T2-321**	■	■	■		■		
Handle mechanisms	**V4-T2-427**	■	■	■		■		
Handle extension ③	**V4-T2-442**		■			■		
OPTIM System Components								
Breaker interface module (BIM)	**V4-T2-327**	●	●	●				
Digitrip OPTIMizer	**V4-T2-327**	●	●	●				
Auxiliary power module	**V4-T2-327**	●	●	●				
Modifications (Refer to Eaton)								
Special calibration	—	●	●	●	●	●	●	●
Moisture fungus treatment	**V4-T2-116**	●	●	●	●	●	●	●
Freeze-tested circuit breakers	—	●	●	●	●	●	●	●
Marine/naval application	—	●	●	●	●	●	●	●

Legend

■ Applicable in indicated pole position

● Accessory available/modification available

Notes

① All accessories mount in the RH cavity which will accept one each shunt trip, UVR, auxiliary switch and alarm switch.

② Mounts outside breaker.

③ Included with breaker.

Technical Data and Specifications

UL 489/CSA Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	277	480	600
RD	3, 4	125	—	65	50
CRD ②	3	125	—	65	50
RDC	3, 4	200	—	100	65
CRDC ②	3	200	—	100	65

IEC 947-2 Interrupting Capacity Ratings ①

Circuit Breaker Type	Number of Poles	Interrupting Capacity (kA Symmetrical Amperes) Volts AC (50/60 Hz) 240	415	690
RD				
I_{cu}	3, 4	135	70	25
I_{cs}	3, 4	100	50	13
RDC				
I_{cu}	3, 4	200	100	35
I_{cs}	3, 4	100	50	18

Notes

① Utilization Category A circuit breakers.

② 100% rated breakers.

See **Page V4-T2-253** for Trip Unit Specifications.

Specifications

R-Frame Digitrip

Trip Unit Type	Digitrip RMS 510	Digitrip RMS 610	Digitrip RMS 810	Digitrip RMS 910	Digitrip OPTIM 1050
rms sensing	Yes	Yes	Yes	Yes	Yes
Breaker Type					
Frame	R	R	R	R	R
Ampere range	800–2500 A	800–2500 A	800–2500 A	800–2500 A	800–2500 A
Interrupting rating at 480 volts	65, 100 (kA)	65, 100 (kA)	65, 100 (kA)	65, 100 (kA)	65, 100 (kA)
Protection					
Ordering options	LI, LS, LSI, LIG, LSG, LSIG	LI, LS, LSI, LIG, LSG, LSIG	LI, LS, LSI, LIG, LSG, LSIG	LI, LS, LSI, LIG, LSG, LSIG	LSI(A), LISG
Fixed rated plug (I_n)	Yes	Yes	Yes	Yes	Yes
Overtemperature trip	Yes	Yes	Yes	Yes	Yes
Long Delay Protection (L)					
Adjustable rating plug (I_n)	No	No	No	No	No
Long delay pickup	0.5–1.0 x (I_n)	0.5–1.0 x (I_n)	0.5–1.0 x (I_n)	0.5 –1.0 x (I_n)	0.4–1.0 x (I_n)
Long delay time I^2t	2–24 seconds	2–24 seconds	2–24 seconds	2–24 seconds	2–24 seconds
Long delay time I^4t	No	No	No	No	1–5 Seconds
Long delay thermal memory	Yes	Yes	Yes	Yes	Yes
High load alarm	No	0.85 x I_r	0.85 x I_r	0.85 x I_r	0.5-1.0 x I_r
Short Delay Protection (S)					
Short delay pickup	200–600% S1 and S2 x (I_r)	200–600% S1 and S2 x (I_r)	200–600% S1 and S2 x (I_r)	200–600% S1 and S2 x (I_r)	150-800% x (I_r) ①②
Short delay time I^2t	100–500 ms	100–500 ms	100–500 ms	100–500 ms	100–500 ms
Short delay time flat	100–500 ms	100–500 ms	100–500 ms	100–500 ms	100–500 ms
Short delay time zone selective interlocking	Yes	Yes	Yes	Yes	Yes
Instantaneous Protection (I)					
Instantaneous pickup	200–600% M1and M2 x (I_n)	200–600% M1and M2 x (I_n)	200–600% M1and M2 x (I_n)	200–600% M1and M2 x (I_n)	200–800% x (I_n) ②
Discriminator	Yes ③	Yes ③	Yes ③	Yes ③	Yes
Instantaneous override	Yes	Yes	Yes	Yes	Yes
Ground Fault Protection (G)					
Ground fault alarm ④	No	No	No	No	25–100% x (I_n)
Ground fault pickup ④	25–100% x (I_s)	25-100% x (I_s)	25–100% x (I_s)	25–100% x (I_s)	25–100% x (I_n)
Ground fault delay I^2t	100–500 ms	100–500 ms	100–500 ms	100–500 ms	100–500 ms
Ground fault delay flat	100–500 ms	100–500 ms	100 –500 ms	100–500 ms	100–500 ms
Ground fault zone selective interlocking	Yes	Yes	Yes	Yes	Yes
Ground fault thermal memory	Yes	Yes	Yes	Yes	Yes

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting x I_n

Notes

① Except 2500 ampere frame is 200–600%.
② Varies by frame.
③ LS/LSG only.
④ Not to exceed 1200 amperes.

R-Frame Digitrip, continued

Trip Unit Type	Digitrip RMS 510	Digitrip RMS 610	Digitrip RMS 810	Digitrip RMS 910	Digitrip OPTIM 1050
System Diagnostics					
Status LEDs	Yes	Yes	Yes	Yes	Yes
Cause of trip LEDs	Yes	Yes	Yes	Yes	Yes
Magnitude of trip information	No	Yes	Yes	Yes	Yes
Remote signal contacts	No	Yes	Yes	Yes	Yes
System Monitoring					
Digital display	No	Yes	Yes	Yes	Yes ①
Current	No	Yes	Yes	Yes	Yes
Voltage	No	No	No	Yes	No
Power and energy	No	No	Yes	Yes	Yes
Power quality—harmonics	No	No	No	Yes	Yes
Power factor	No	No	Yes (over Eaton PowerNet only)	Yes	Yes
Communications					
Eaton PowerNet	No	No	Yes	Yes	Yes
Testing					
Testing method	Integral	Integral	Integral	Integral	OPTIMizer, BIM, PowerNet

Legend

BIM = Breaker Interface Module
(A) = GF Alarm
I_s = Sensor Rating
I_n = Rating Plug
I_r = Long Delay Pickup Setting x I_n

Note

① By OPTIMizer/BIM.

Dimensions and Weights

Dimensions in Inches (mm)

RD Frame

Number of Poles	Width	Height	Depth
3	15.50 (393.7)	16.00 (406.4)	9.75 (247.7)
4	20.00 (508.0)	16.00 (406.4)	9.75 (247.7)

RD-Frame, Three-Pole, 1600 and 2000 Amperes



Approximate Shipping Weight in Lbs (kg)

RD Frame

Breaker Type	Complete Breaker Three-Pole	Four-Pole
1600 Amperes		
RD, CRD ①, RDC, CRDC ①	102 (46.3)	135 (61.2)
2000 Amperes		
RD, RDC	102 (46.3)	135 (61.2)
CRD, CRDC	130 (59.0)	175 (79.4)
2500 Amperes		
RD, RDC	135 (61.2)	182 (82.6)

Note

① No four-pole for CRD and CRDC.

Motor Circuit Protectors

2

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	
Catalog Number Selection	**V4-T2-257**
Product Selection	**V4-T2-258**
Accessories	**V4-T2-259**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Motor Circuit Protectors (MCP)

Product Description

Designated as Eaton's Types GMCP and HMCP, the instantaneous-only motor circuit protector (MCP) is available in ratings from 3 A to 1200 A for motor starter sizes 0 through 8.

An innovative design of internal components allows higher MCP-starter combination interrupting ratings. The MCP is marked to permit proper electrical application within the assigned equipment ratings.

Standards and Certifications

The MCP is designed to comply with the applicable requirements of Underwriters Laboratories Standard UL 489, Canadian Standards Association Standard C22.2 No. 5.1, and International Electrotechnical Commission Recommendations IEC 157-1.

The MCP is a recognized component (UL File E7819) and complies with the applicable requirements of Underwriters Laboratories Standard UL 489. It is also designed to comply with the applicable requirements of Canadian Standards Association Standard C22.2 No. 5.1, International Electrotechnical Commission Recommendations IEC 157-1, and nameplates bear the CE marking.

Listed

Note: Interrupting ratings are dependent on starter it is used with.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

Motor Circuit Protector

HMCP 003 A0 C

Motor Circuit Protective Type
HMCP = Three-pole
HM2P = Two-pole ①
HMCPS = Three-pole

Continuous Ampere Rating
003
007
015
025
030
050
070
100
150
250
400
600
800
1200

Magnetic Trip Range/ NEMA Starter Size
A0 = 9–30/0
C0 = 21–70/0
E0 = 45–150/0
D0 = 40–60/0
H1 = 90–300/1
G2 = 80–120/2
K2 = 50–500/2
J2 = 115–170/2
M2 = 210–700/2
L3 = 160–240/3
R3 = 300–1000/3
T4 = 450–1500/4
U4 = 750–2500/4
A5 = 350–700/5
C5 = 450–900/5
D5 = 500–1000/5
F5 = 625–1250/5
G5 = 750–1500/5
J5 = 875–1750/5
K5 = 1000–2000/5
L5 = 1125–2250/5
W5 = 1250–2500/5
N5 = 1500–3000/5
R5 = 1750–3500/5
X5 = 2000–4000/5
Y5 = 2250–4500/5
L6 = 1800–6000/6 (electronic)
X6 = 500–2500/6 (electronic)
Y6 = 1000–4000/6 (electronic)
X7 = 1600–6400/7 (electronic)
Y8 = 2400–9600/8 (electronic)

Suffix
C = Non-aluminum terminals
W = Without terminals
X = Load terminals only
Y = Line terminals only
S = Stainless steel terminals (150A frame only)
No Suffix: Standard terminals on line and load

Motor Circuit Protector

GMCP 003 A0 C

Motor Circuit Protective Device
GMCP = Three-pole

Continuous Ampere Rating
003
007
015
030
050
060
063

Magnetic Trip Range/NEMA Starter Size
A0 = 15–30/0
C0 = 35–70/0
E0 = 75–150/0
H1 = 150–300/1
K2 = 250–500/2
J2 = 300–600/2
M2 = 320–630/2

Suffix
C = Non-aluminum terminals

Note

① On J- and K-Frame HMCPs only.

Product Selection

G-Frame

480 Vac Maximum, 600Y/347 Vac

NEMA Starter Size	Continuous Amperes	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting	MCP Catalog Number
0	3	A	1.1–1.2	15	**GMCP003A0C**
		B	1.3–1.5	18	
		C	1.6–1.7	21	
		D	1.8–1.9	24	
		E	2.0–2.2	27	
		F	2.3–2.5	30	
0	7	A	2.6–3.1	35	**GMCP007C0C**
		B	3.2–3.6	42	
		C	3.7–3.9	49	
		D	4.3–4.7	56	
		E	4.8–5.2	63	
		F	5.3–5.7	70	
0	15	A	5.7–6.8	75	**GMCP015E0C**
		B	6.9–7.9	90	
		C	8.0–9.1	105	
		D	9.2–10.3	120	
		E	10.4–11.4	135	
		F	11.5–12.6	150	
1	30	A	11.5–13.7	150	**GMCP030H1C**
		B	13.8–16.0	180	
		C	16.1–18.3	210	
		D	18.4–20.6	240	
		E	20.7–22.9	270	
		F	23.0–25.2	300	
2	50	A	19.3–22.9	250	**GMCP050K2C**
		B	23.0–26.8	300	
		C	26.9–30.6	350	
		D	30.7–34.5	400	
		E	34.6–38.3	450	
		F	38.4–42.1	500	
3	60	A	23.1–27.5	300	**GMCP060J2C**
		B	27.7–32.2	360	
		C	32.3–36.7	420	
		D	36.9–41.4	480	
		E	41.5–46.0	540	
		F	46.2–50.5	600	
3	63	A	24.2–32.1	320	**GMCP063M2C**
		B	29.1–34.8	380	
		D	38.8–46.4	500	
		E	43.6–48.9	570	
		F	48.5–53.7	630	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 x the minimum FLA value shown. Where a 13 x setting is required for an intermediate FLA value, alternate Cam settings and/or MCP ratings should be used.

All GMCP 3–63A come with line and load steel body terminals for Cu only wire. Refer to **Page V4-T2-122** under Optional Terminal Types.

UL recognized and CSA approved.

Accessories

Modifications for GMCP

Internal accessories must be factory installed.

Internal Accessories ①

Type Accessory	Electrical Ratings Volts	Frequency	Amperes	Contact Arrangement	Factory Suffix	Style Number
Shunt trip ②	120	50/60 Hz	1.1	—	S5	**1373D62G18**
Shunt trip ②	240	50/60 Hz	2.1	—	S6	**1373D62G19**
Auxiliary switch ③	240	50/60 Hz	6.0	1A/1B	A3	**1288C74G03**
Auxiliary switch ③	240	50/60 Hz	6.0	2A/2B	A6	**1288C73G03**
Alarm switch ③	240	50/60 Hz	6.0	Make/Break	B3	**1288C75G03**
Auxiliary switch/alarm switch combination ③	240	50/60 Hz	6.0	1A/1B Make/Break	B13	**1288C76G09**

External Mounted Accessories

Description	Number Units in Package	Style Number
Lock dog (non-padlockable)	1	**1294C01H01**
Mounting hardware	1	**624B375G23**
DIN rail adapter ④	10	**1225C79G02**

Modifications for HMCP

See Internal Accessories starting on **Page V4-T2-273**.

Handle Mechanisms for Series C Frames

Kits Only (Kit Includes Shaft, Mechanism and Handle)—GMCP-Frame

	Description	Rating Type NEMA	IP	GMCP-Frame Catalog Number
S01 Blue Handle	S01 blue handle, 12-inch shaft	1/3R/12	54	**GMHMVD12B / 68C6039G05**
		4/4X	65	**GMHMVD12BX / 68C6039G07**
S01 Red Handle	S01 red handle, 12-inch shaft	1/3R/12	54	**GMHMVD12R / 68C6039G06**
		4/4X	65	**GMHMVD12RX / 68C6039G08**

Direct (Close-Coupled) Handle Mechanisms

G Direct ⑤

Frame	Black Handle With Shroud Catalog Number	Black Handle Without Shroud Catalog Number	Yellow Handle With Shroud Catalog Number	Yellow Handle Without Shroud Catalog Number
GMCP	**HRGMC1S**	**HRGMC10**	**HRGMC3S**	**HRGMC30**

Notes

① Only one accessory may be installed in GMCP.
② LH only.
③ RH only.
④ For use with standard 35 mm DIN rail such as, 35 x 7.5 or 15 mm per DIN EN50022.
⑤ Suitable for use on two- or three-pole G-Frame.

No UVR available on GMCP.

F-Frame

600 Vac Maximum, 250 Vdc Maximum

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number
0	3	A	0.69–0.91	9	**HMCP003A0C**
		B	0.92–1.0	12	
		C	1.1–1.2	15	
		D	1.3–1.5	18	
		E	1.6–1.7	21	
		F	1.8–1.9	24	
		G	2.0–2.2	27	
		H	2.3–2.5	30	
0	7	A	1.5–2.0	21	**HMCP007C0C**
		B	2.1–2.5	28	
		C	2.6–3.1	35	
		D	3.2–3.6	42	
		E	3.7–3.9	49	
		F	4.3–4.7	56	
		G	4.8–5.2	63	
		H	5.3–5.7	70	
0	15	A	3.4–4.5	45	**HMCP015E0C**
		B	4.6–5.6	60	
		C	5.7–6.8	75	
		D	6.9–7.9	90	
		E	8.0–9.1	105	
		F	9.2–10.3	120	
		G	10.4–11.4	135	
		H	11.5 –12.6	150	
1	30	A	6.9–9.1	90	**HMCP030H1C**
		B	9.2–11.4	120	
		C	11.5–13.7	150	
		D	13.8–16.0	180	
		E	16.1–18.3	210	
		F	18.4–20.6	240	
		G	20.7–22.9	270	
		H	23.0–25.2	300	
2	50	A	11.5–15.2	150	**HMCP050K2C**
		B	15.3–19.1	200	
		C	19.2–22.9	250	
		D	23.0–26.8	300	
		E	26.9–30.6	350	
		F	30.7–4.5	400	
		G	34.6–38.3	450	
		H	38.4–42.1	500	

600 Vac Maximum, 250 Vdc Maximum, continued

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number
2	70	A	16.1–21.4	210	**HMCP070M2C**
		B	21.5 –26.8	280	
		C	26.9 –32.2	350	
		D	32.3–37.5	420	
		E	37.6–42.9	490	
		F	43.0–48.3	560	
		G	48.4–53.7	630	
		H	53.8–59.1	700	
3	100	A	23.0–30.6	300	**HMCP100R3C**
		B	30.7–38.3	400	
		C	38.4–46.0	500	
		D	46.1–53.7	600	
		E	53.8 –61.4	700	
		F	61.5 –69.1	800	
		G	69.2–76.8	900	
		H	76.9–84.5	1000	
4	150	A	34.6–46.0	450	**HMCP150T4C**
		B	46.1–57.5	600	
		C	57.6–69.1	750	
		D	69.2–80.6	900	
		D	69.2–80.6	900	
		E	80.7–92.2	1050	
		F	92.3–103.7	1200	
		G	103.8–115.2	1350	
		H	115.3–126.7	1500	
4	150	A	57.0 –75.0	750	**HMCP150U4C**
		B	76.0–95.0	1000	
		C	96.0–114.0	1250	
		D	115.0–130.7	1500	
		E	③	1750	
		F	③	2000	
		G	③	2250	
		H	③	2500	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 x the minimum FLA value shown. Where a 13 x setting is required for an intermediate FLA value, alternate Cam settings and/or MCP ratings should be used.

② For DC applications, actual trip levels are approximately 40% higher than values shown.

③ Settings above 130 amperes are for special applications. NEC Article 430.110(a) requires the ampere rating of the disconnecting means to be not less than 115% of the motor full load ampere rating.

HMCP 3–100 A come with line and load steel body terminals, 3T100FB. HMCP 150A come with line and load steel body terminals, 3T150FB.

Special Low Magnetic Protection Application MCP

600 Vac Maximum, 250 Vdc Maximum

Cont. Amps	Cam Setting	MCP Trip Setting ①	MCP Catalog Number
25	A	40	**HMCP025D0C**
	B	43	
	D	49	
	E	52	
	F	55	
	G	58	
	H	60	
50	A	80	**HMCP050G2C**
	B	87	
	C	93	
	D	98	
	E	103	
	F	109	
	G	115	
	H	120	
70	A	115	**HMCP070J2C**
	B	122	
	C	130	
	D	139	
	E	145	
	F	153	
	G	160	
	H	170	
100	A	160	**HMCP100L3C**
	B	174	
	C	185	
	D	196	
	E	207	
	F	218	
	G	229	
	H	240	

Notes

① For DC applications, actual trip levels are approximately 40% higher than values shown.

HMCP 25–100 A come with line and load steel body terminals, 3T100FB.

MCPs for Application with Motor Starters Equipped with Electronic Overload Relays

600 Vac Maximum, 250 Vdc Maximum

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number
0	3	A	0.69–0.91	9	**HMCPS003A0C**
		B	0.92–1.0	12	
		C	1.1–1.2	15	
		D	1.3–1.5	18	
		E	1.6–1.7	21	
		F	1.8–1.9	24	
		G	2.0–2.2	27	
		H	2.3–2.5	30	
0	7	A	1.5–2.0	21	**HMCPS007C0C**
		B	2.1–2.5	28	
		C	2.6–3.1	35	
		D	3.2–3.6	42	
		E	3.7–3.9	49	
		F	4.3–4.7	56	
		G	4.8–5.2	63	
		H	5.3–5.7	70	
0	15	A	3.4–4.5	45	**HMCPS015E0C**
		B	4.6–5.6	60	
		C	5.7–6.8	75	
		D	6.9–7.9	90	
		E	8.0–9.1	105	
		F	9.2–10.3	120	
		G	10.4–11.4	135	
		H	11.5–12.6	150	
1	30	A	6.9–9.1	90	**HMCPS030H1C**
		B	9.2–11.4	120	
		C	11.5–13.7	150	
		D	13.8–16.0	180	
		E	16.1–18.3	210	
		F	18.4–20.6	240	
		G	20.7–22.9	270	
		H	23.0–25.2	300	
2	50	A	11.5–15.2	150	**HMCPS050K2C**
		B	15.3–19.1	200	
		C	19.2–22.9	250	
		D	23.0–26.8	300	
		E	26.9–30.6	350	
		F	30.7–34.5	400	
		G	34.6–38.3	450	
		H	38.4–42.1	500	

600 Vac Maximum, 250 Vdc Maximum, continued

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number
3	100	A	23.0–30.6	300	**HMCPS100R3C**
		B	30.7–38.3	400	
		C	38.4–46.0	500	
		D	46.1–53.7	600	
		E	53.8–61.4	700	
		F	61.5–69.1	800	
		G	69.2–76.8	900	
		H	76.9–84.5	1000	
4	150	A	34.6–46.0	450	**HMCPS150T4C**
		B	46.1–57.5	600	
		C	57.6–69.1	750	
		D	69.2–80.6	900	
		E	80.7–92.2	1050	
		F	92.3–103.7	1200	
		G	103.8–115.2	1350	
		H	115.3–126.7	1500	
4	150	A	57.0–75.0	750	**HMCPS150U4C**
		B	76.0–95.0	1000	
		C	96.0–114.0	1250	
		D	115.0–130.7	1500	
		E	③	1750	
		F	③	2000	
		G	③	2250	
		H	③	2500	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 x the minimum FLA value shown. Where a 13 x setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

② For DC applications, actual trip levels are approximately 40% higher than values shown.

③ Settings above 130A are for special applications. NEC Article 430.110(a) requires the ampere rating of the disconnecting means to be not less than 115% of the motor full load ampere rating.

HMCP 25–100 A come with line and load steel body terminals, 3T100FB.

HMCPS 3–100 A come with line and load steel body terminals, 3T100FB. HMCPS 150A come with line and load steel body terminals, 3T150FB.

J-Frame

600 Vac Maximum, 250 Vdc Maximum

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number ③
4	250	A	27.0–30.7	350	**HMCP250A5C**
		B	30.8–33.8	400	
		C	33.9–36.9	440	
5	250	D	37.0–40.3	480	
		E	40.4–43.8	525	
		F	43.9–46.9	570	
		G	47.0–50.7	610	
		H	47.0–50.7	660	
		I	47.0–50.7	700	
5	250	A	34.7–38.8	450	**HMCP250C5C**
		B	38.9–43.4	505	
		C	43.5–47.6	565	
		D	47.7–52.2	620	
		E	52.3–56.5	680	
		F	56.6–60.7	735	
		G	60.8–64.9	790	
		H	65.0–69.2	845	
		I	69.3–73.5	900	
5	250	A	38.5–43.4	500	**HMCP250D5C**
		B	43.5–48.0	565	
		C	48.1–53.0	625	
		D	53.1–57.6	690	
		E	57.7–62.3	750	
		F	62.4–67.3	810	
		G	67.4–71.9	875	
		H	72.0–76.9	935	
		I	77.0–81.6	1000	
5	250	A	48.1–53.8	625	**HMCP250F5C**
		B	53.9–59.9	700	
		C	60.0–66.1	780	
		D	66.2–72.3	860	
		E	72.4–78.4	940	
		F	78.5–83.8	1020	
		G	83.9–89.9	1090	
		H	90.0–96.1	1170	
		I	96.2–102.0	1250	
5	250	A	57.7–64.6	750	**HMCP250G5C**
		B	64.7–71.9	840	
		C	72.0–79.2	935	
		D	79.3–86.5	1030	
		E	86.6–93.8	1125	
		F	93.9–101.1	1220	
		G	101.2–108.4	1315	
		H	108.5–115.3	1410	
		I	115.4–122.4	1500	

600 Vac Maximum, 250 Vdc Maximum, continued

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number ③
5	250	A	67.4–75.3	875	**HMCP250J5C**
		B	75.4–83.8	980	
		C	83.9–92.3	1090	
		D	92.4–100.7	1200	
		E	100.8–109.2	1310	
		F	109.3–117.6	1420	
		G	117.7–126.1	1530	
		H	126.2–134.6	1640	
		I	134.7–142.8	1750	
5	250	A	77.0–86.6	1000	**HMCP250K5C**
		B	86.6–96.1	1125	
		C	96.2–105.7	1250	
		D	105.8–115.3	1375	
		E	115.4–124.9	1500	
		F	125.0–134.6	1625	
		G	134.7–144.2	1750	
		H	144.3–153.8	1875	
		I	153.9–163.3	2000	
5	250	A	86.6–97.3	1125	**HMCP250L5C**
		B	97.4–108.4	1265	
		C	108.5–118.8	1410	
		D	118.9–129.9	1545	
		E	130.0–140.7	1690	
		F	140.8–151.5	1830	
		G	151.6–162.3	1970	
		H	162.4–173.0	2110	
		I	173.1–183.6	2250	
5	250	A	96.2–108.0	1250	**HMCP250W5C**
		B	108.1–119.9	1405	
		C	120.0–132.3	1560	
		D	132.4–144.2	1720	
		E	144.3–156.1	1875	
		F	156.2–168.0	2030	
		G	168.1–179.9	2185	
		H	180.0–192.3	2340	
		I	192.4–204.0	2500	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 times the minimum FLA value shown. Where a 13 times setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

② For DC applications, actual trip levels are approximately 40% higher than values shown.

③ Three-pole catalog numbers shown. Two-pole catalog numbers begin with **HM2P** in place of **HMCP**.

All HMCP and HM2P 250A come with line and load steel body terminals, T250KB. (With suffix "C," without "C" comes with TA250KB.)

K-Frame

2

600 Vac Maximum, 250 Vdc Maximum

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number ③
4	400	A	27.0–30.7	350	**HMCP400A5C**
		B	30.8–33.8	400	
		C	33.9–36.9	440	
5	400	D	37.0–40.3	480	**HMCP400A5C**
		E	40.4–43.8	525	
		F	43.9–46.9	570	
		G	47.0–50.7	610	
		H	50.8–53.8	660	
		I	53.9–57.2	700	
5	400	A	38.5–43.4	500	**HMCP400D5C**
		B	43.5–48.0	565	
		C	48.1–53.0	626	
		D	53.1–57.6	690	
		E	57.7–62.3	750	
		F	62.4–67.3	810	
		G	67.4–71.9	875	
		H	72.0–76.9	935	
		I	77.0–81.6	1000	
5	400	A	48.1–53.8	625	**HMCP400F5C**
		B	53.9–59.9	700	
		C	60.0–66.1	780	
		D	66.2–72.3	860	
		E	72.4–78.4	940	
		F	78.5–83.8	1020	
		G	83.9–89.9	1090	
		H	90.0–96.1	1170	
		I	96.2–102.0	1250	
5	400	A	57.7–64.6	750	**HMCP400G5C**
		B	64.7–71.9	840	
		C	72.0–79.2	935	
		D	79.3–86.5	1030	
		E	86.6–93.8	1125	
		F	93.9–101.1	1220	
		G	101.2–108.4	1315	
		H	108.5–115.3	1410	
		I	115.4–122.4	1500	
5	400	A	67.4–75.3	875	**HMCP400J5C**
		B	75.4–83.8	980	
		C	83.9–92.3	1090	
		D	92.4–100.7	1200	
		E	100.8–109.2	1310	
		F	109.3–117.6	1420	
		G	117.7–126.1	1530	
		H	126.2–134.6	1640	
		I	134.7–142.8	1750	

600 Vac Maximum, 250 Vdc Maximum, continued

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number ③
5	400	A	77.0–86.5	1000	**HMCP400K5C**
		B	86.6–96.1	1125	
		C	96.2–105.7	1250	
		D	105.8–115.3	1375	
		E	115.4–124.9	1500	
		F	125.0–134.6	1625	
		G	134.7–144.2	1750	
		H	144.3–153.8	1875	
		I	153.9–163.3	2000	
5	400	A	86.6–97.3	1125	**HMCP400L5C**
		B	97.4–108.4	1265	
		C	108.5–118.8	1410	
		D	118.9–129.9	1545	
		E	130.0–140.7	1690	
		F	140.8–151.5	1830	
		G	151.6–162.3	1970	
		H	162.4–173.0	2110	
		I	173.1–183.6	2250	
5	400	A	96.2–108.0	1250	**HMCP400W5C**
		B	108.1–119.9	1405	
		C	120.0–132.3	1560	
		D	132.4–144.2	1720	
		E	144.3–156.1	1875	
		F	156.2–168.0	2030	
		G	168.1–179.9	2185	
		H	180.0–192.3	2340	
		I	192.4–204.0	2500	
5	400	A	115.4–129.9	1500	**HMCP400N5C**
		B	130.0–144.2	1690	
		C	144.3–158.4	1875	
		D	158.5–173.0	2060	
		E	173.1–187.6	2250	
		F	187.7–201.9	2440	
		G	202.0–216.1	2625	
		H	216.2–230.7	2810	
		I	230.8–244.9	3000	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 x the minimum FLA value shown. Where a 13 x setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

② For DC applications, actual trip levels are approximately 40% higher than values shown.

③ Three-pole catalog numbers shown. Two-pole catalog numbers begin with **HM2P** in place of **HMCP**.

All HMCP and HM2P 400 A come with aluminum body terminals, 3TA400K. Catalog numbers with suffix "C" as shown above come with copper body terminals 3T400K.

600 Vac Maximum, 250 Vdc Maximum, continued

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting ②	MCP Catalog Number ③
5	400	A	134.7–151.5	1750	**HMCP400R5C**
		B	151.6–168.4	1970	
		C	168.5–185.3	2190	
		D	185.4–201.9	2410	
		E	202.0–218.8	2625	
		F	218.9–235.7	2845	
		G	235.8–252.6	3065	
		H	252.7–269.2	3285	
		I	269.3–285.7	3500	
5	400	A	153.9–173.0	2000	**HMCP400X5C**
		B	173.1–192.3	2250	
		C	192.4–211.5	2500	
		D	211.6–230.7	2750	
		E	230.8–249.9	3000	
		F	250.0–269.2	3250	
		G	269.3–288.4	3500	
		H	288.5–307.6	3750	
		I	307.7–326.9	4000	
5	400	A	173.1–194.5	2250	**HMCP400Y5C**
		B	194.6–216.1	2530	
		C	216.2–237.6	2810	
		D	237.7–259.5	3090	
		E	259.6–281.1	3375	
		F	281.2–302.6	3655	
		G	302.7–324.1	3935	
		H	324.2–346.1	4215	
		I	346.2–368.1	4500	

L-Frame

600 Vac Maximum ④

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ①	MCP Trip Setting	MCP Catalog Number
6	600	A	138.5–184.5	1800	**HMCP600L6W**
		B	184.6–230.7	2400	
		C	230.8–276.8	3000	
		D	276.9–323.0	3600	
		E	323.1–369.1	4200	
		F	369.2–415.3	4800	
		G	415.4–461.4	5400	
		H	461.5–507.7	6000	
6	600	A	38.5–46.1	500	**HMCP600X6W**
		B	46.2–61.4	600	
		C	61.5–76.8	800	
		D	76.9–96.1	1000	
		E	96.2–115.3	1250	
		F	115.4–153.7	1500	
		G	153.8–192.2	2000	
		H	192.3–230.7	2500	
6	600	A	76.9–96.1	1000	**HMCP600Y6W**
		B	96.2–115.3	1250	
		C	115.4–153.7	1500	
		D	153.8–192.2	2000	
		E	192.3–230.7	2500	
		F	230.8–269.1	3000	
		G	269.2–307.6	3500	
		H	307.7–346.1	4000	

Notes

① Motor FLA ranges are typical. The corresponding trip setting is at 13 x the minimum FLA value shown. Where a 13 x setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

② For DC applications, actual trip levels are approximately 40% higher than values shown.

③ Three-pole catalog numbers shown. Two-pole catalog numbers begin with **HM2P** in place of **HMCP**.

④ Equipped with electronic trip device.

All HMCP and HM2P 400 A come with aluminum body terminals, 3TA400K. Catalog numbers with suffix "C" as shown above come with copper body terminals 3T400K.

All HMCP 600 A come without terminals. For terminals, see **Page V4-T2-217.**

N-Frame

2

600 Vac Maximum ①

NEMA Starter Size	Cont. Amps	Cam Setting	Motor Full Load Current Amperes (FLA) ②	MCP Trip Setting	MCP Catalog Number
7	800	A	123.1–184.5	1600	**HMCP800X7W**
		B	184.6–246.1	2400	
		C	246.2–307.6	3200	
		D	307.7–369.1	4000	
		E	369.2–430.7	4800	
		F	430.8–492.2	5600	
		G	492.3–553.7	6400	
8	1200	A	184.6–276.8	2400	**HMCP12Y8W**
		B	276.9–369.1	3600	
		C	369.2–461.4	4800	
		D	461.5–553.7	6000	
		E	553.8–646.1	7200	
		F	646.2–738.4	8400	
		G	738.5–830.7	9600	

Notes

① Equipped with electronic trip device.

② Motor FLA ranges are typical. The corresponding trip setting is at 13X the minimum FLA value shown. Where a 13X setting is required for an intermediate FLA value, alternate cam settings and/or MCP ratings should be used.

Motor Protection Circuit Breakers

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	
Product Selection	**V4-T2-268**
Technical Data and Specifications	**V4-T2-268**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Motor Protection Circuit Breakers (MPCB)

Product Description

Motor protection circuit breakers (MPCBs) provide UL 489 branch circuit protection, UL 508 and CSA C22.2 No. 14 motor protection, and meet IEC 60947-2 and 50947-4 requirements. Typical branch motor loads are protected by three-component starters, consisting of breaker, contactor and overload relay, or fuse, contactor and overload relay. The MPCB application-specific protection eliminates the need for motor overload relay found in the traditional three-component starter assembly. The branch motor load protection is simplified to an MPCB and contactor, reducing both space requirements and heat generation in customer panels. Protection is provided by application-specific electronic trip units.

The electronic trip unit provides typical motor overload relay functionality and short-circuit protection against potential phase-to-phase or phase-to-ground faults.

- Disconnecting means
- Branch circuit short-circuit protection
- Overload protection
  - Class 5, 10, 15 and 20
- Phase unbalance protection
  - FDMP breaker trips when there is a 40% difference between any phase compared to the calculated three-phase average
- Phase loss protection
  - Active when the maximum phase current is greater than 50% of FLA setting
  - Breaker will trip when minimum phase current is 25% or less than the maximum phase current
  - Time delay of 1 or 2 seconds before breaker trips
- Thermal memory to prevent immediate restart after overload trip to allow motor to cool down

The MPCB is based on the Series C F-Frame. Accessories for standard Series C breakers apply to the MPCB. Unlike Motor Circuit Protectors (MCPs), MPCBs are UL 489 listed with 35 kA and 65 kA interruption ratings.

Product Selection

FDMP and HFDMP

Continuous Amperes	35 kA Without Phase Unbalance, Class 10 Motor Protection Only	35 kA With Phase Unbalance and Adjustable Motor Class Protection	65 kA Without Phase Unbalance, Class 10 Motor Protection Only	65 kA With Phase Unbalance and Adjustable Motor Class Protection
80	**FDMP3080L**	**FDMP3080JL**	**HFDMP3080L**	**HFDMP3080JL**
100	**FDMP3100L**	**FDMP3100JL**	**HFDMP3100L**	**HFDMP3100JL**
160	**FDMP3160L**	**FDMP3160JL**	**HFDMP3160L**	**HFDMP3160JL**
205	**FDMP3205L**	**FDMP3205JL**	**HFDMP3205L**	**HFDMP3205JL**

FLA Ie Dial Setting

Continuous Amperes	A	B	C	D	E	F	G	H
80	40	50	60	70	80	—	—	—
100	80	—	90	—	100	—	—	—
160	100	115	130	145	160	—	—	—
205	160	170	180	195	205	—	—	—

Technical Data and Specifications

Specifications

Feature	FDMP	HFDMP
Interruption rating at 240 V	65 kA	100 kA
Interruption rating at 480 V	35 kA	65 kA
Interruption rating at 600 V	18 kA	25 kA
Icu/Ics at 240 V	65 kA/33 kA ①	100 kA/50 kA ①
Icu/Ics at 415 V	35 kA/18 kA ①	65 kA/33 kA ①
100% rated	No	No
FLA range (A)	40–205	40–205
Motor class protection	5, 10, 15, 20	5, 10, 15, 20
Phase unbalance protection (current)—active for phase current >0.5 FLA setting	□40% delta (single-phase): (three-phase avg.) for 5 seconds	□40% delta (single-phase): (three-phase avg.) for 5 seconds
Phase loss protection (current)—active for phase current >0.5 FLA setting	Min. phase □0.25 max. phase for 1 second	Min. phase □0.25 max. phase for 1 second
Thermal memory protection	Yes	Yes
High load indicator	—	—
Pre-detection relays	—	—
Internal accessories	Factory installed	Factory installed
	Aux. alarm, shunt trip, UVR	Aux. alarm, shunt trip, UVR

Notes

① IEC ratings available only on FWMP and HFWMP.

For additional breaker solutions, see **Page V4-T2-89**.

Type ELC Current Limiter Attachment

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4) Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Type ELC Current Limiter Attachment (Size 0–4)

Product Description

Eaton's Type ELC current limiter attachment for the MCP is designed to provide increased interrupting capacity. The combination may be used for the application up to 200,000 A symmetrical at 600 Vac, making the MCP suitable for use in network distribution systems or other applications where unusually high fault currents are available. The current limiter connects to the load end of the MCP and is provided with terminals suitable for copper or aluminum conductors. (See table at right.)

Limiters are coordinated with the MCP so that normal fault currents are interrupted automatically by the MCP without any damage to the limiter. Only the rare very high fault is opened by the limiter. Faults that are interrupted by the limiter also magnetically trip the MCP, opening all three poles, preventing single-phase operation.

Each of the three poles of the Type ELC limiter is equipped with an indicator that extends when a fault is interrupted by the limiter.

Product Selection

Type ELC Current Limiter Attachment

ELC Current Limiter Attachment

MCP Rating (Amperes)	Catalog Number
3	**ELC3003R**
7	**ELC3007R**
15	**ELC3015R**
30	**ELC3030R**
50	**ELC3050R**
100	**ELC3100R**
150	**ELC3150R**

Technical Data and Specifications

Type ELC Current Limiter Terminal Wire Sizes ①

Type ELC Current Limiter Maximum Amperes	Wire Range AWG	Metric (mm^2)
Standard Aluminum Terminals		
50	14–2	2.5–35
100	1–4/0	50–95
150	1–4/0	50–95
Non-Standard Terminals (Steel)		
50	14–2 ②	2.5–35
100	—	—
150	—	—

Notes

① Terminal wire connectors are UL listed for standard stranded wire sizes as defined in UL 486A or UL 486B.

② Optional on special order for copper cable only.

All HMCP 800 A and 1200 A come without terminals. For terminals, see **Page V4-T2-217.**

Current Limiting Circuit Breaker Module

2

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	
Product Selection	**V4-T2-271**
Technical Data and Specifications	**V4-T2-272**
Dimensions and Weights	**V4-T2-272**
Internal Accessories	**V4-T2-273**
External Accessories	**V4-T2-306**

Current Limiting Circuit Breaker Module

Product Overview

Power demand continues to grow in new and existing facilities. To meet increased demand, larger utility supplies, spot networks and large facility transformers are installed. The increased capacity of the electrical source results in increased fault currents in excess of 100 kA short-circuit protection. Eaton manufactures non-fused current limiting modules with interrupting capacities up to 200 kA at 600 Vac. Unlike fused current limiters with a one-time use, a current limiter module provides an automatic reset of the module after a short-circuit event. Resetting the molded-case circuit breaker is the only action required to restore critical power to the system; there is no time wasted with sourcing the correct replacement fuses or module to bring the system back online.

Product Description

The current limiting breaker modules use a unique contact design to enhance the system protection similar to that of the circuit breaker. When high short-circuit current is flowing through the contacts of these modules, the design results in very high interrupting capacities and improved current limiting characteristics.

Application Description

High-performance breakers are most commonly applied when very high fault levels are available and with applications where the current limiting capability is used upstream of the final load to limit current. Typical loads include lighting, power distribution, and motor control applications.

Features and Benefits

Superior system protection:

- Auto reset improves system uptime and eliminates the need for finding replacement parts
- No fuses to replace, reducing the overall cost of ownership and the waste created by fuses
- Overloads, by using inverse time current tripping characteristics of the molded-case circuit breaker
- Low-level short circuits, by using instantaneous and/or short-time delay tripping characteristics of the molded-case circuit breaker
- High-level short circuits, by using ultra-high-speed, blow-apart contacts of the current limiting module in series with the circuit breaker contacts
- Let-through currents, by improved opening speed of the contacts, the resultant rapid rise of arc voltage introduces impedance into the system

Standards and Certifications

- UL 489
- CSA C22.2

Listed

Product Selection

Series C High Performance Ratings

Type	Product	Amperes	480 Vac (UL)	600 Vac (UL)
FDC 3P thermal-magnetic	Breaker only	15–225	100	35
	With limiter	40–200	200	200

FD Frame

FD IC Rating—200 kAIC at 600 Vac ①

Ampere Rating	Breaker with Line Side Mounted Current Limiter ②	Breaker with Load Side Mounted Current Limiter ③
Thermal-Magnetic		
40	**FDC3040Q01**	**FDC3040YQ02**
45	**FDC3045Q01**	**FDC3045YQ02**
50	**FDC3050Q01**	**FDC3050YQ02**
60	**FDC3060Q01**	**FDC3060YQ02**
70	**FDC3070Q01**	**FDC3070YQ02**
80	**FDC3080Q01**	**FDC3080YQ02**
90	**FDC3090Q01**	**FDC3090YQ02**
100	**FDC3100Q01**	**FDC3100YQ02**
110	**FDC3110Q01**	**FDC3110YQ02**
125	**FDC3125Q01**	**FDC3125YQ02**
150	**FDC3150Q01**	**FDC3150YQ02**
175	**FDC3175Q01**	**FDC3175YQ02**
200	**FDC3200Q01**	**FDC3200YQ02**

Limiter Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	Metric Wire Range mm^2	AWG Wire Range/ Number of Conductors	Catalog Number
Standard Pressure Type Terminals					
250	Aluminum	Cu/Al	10–185	#8–350 (1)	**TA250FJ** ④

Breaker Load Terminals (For Line Mounted Limiters Only)

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire Range	Metric Wire Range mm^2	Package of Three Terminals Catalog Number
Standard Pressure Type Terminals					
100	Steel	Cu/Al	14–1/0	2.5–50	**3T100FB**
225	Aluminum	Cu/Al	4–4/0	25–95	**3TA225FD**

Notes

① Line and load terminal included.
② Two interphase barriers provided, mounted on line end of limiter, catalog number **FJ1PBK**.
③ Four interphase barriers provided, (2) line end of breaker, (2) load end of limiter.
④ Load side breaker terminations included for units configured with line mounted limiters.

Technical Data and Specifications

UL 489 Current Limiting Data

Frame	Circuit	Ip (kA)	I^2T (10^6A^2S)
LDC	240 V/200 kA	64.80	6.80
LDC	480 V/100 kA	66.90	9.33
LDC	600 V/50 kA	54.30	8.92

Dimensions and Weights

Approximate Dimensions in Inches (mm)

Assembled Breaker and Current Limiting Module

Frame	Height	Width	Depth	Weight in lbs (kg)
FD + limiter	12.06 (306.3)	4.13 (104.9)	3.39 (86.1)	8.50 (3.86)

FD-Frame With Current Limiter Module



Series C Internal Accessories



Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	
Product Selection	**V4-T2-275**
Technical Data and Specifications	**V4-T2-294**
External Accessories	**V4-T2-306**

Internal Accessories

Product Overview

Alarm Switch

For remote indication of automatic trip operation. Does not function with manual switching; however, it will operate when either a shunt trip or undervoltage release is operated. A "make" contact closes and a "break" contact opens when the alarm/lockout switch operates. The switch automatically resets when the circuit breaker is reset.

Auxiliary Switch

The auxiliary switch provides circuit breaker contact status information by monitoring the position of the molded cross bar that contains the moving contact arms. The auxiliary switch is used for remote indication and interlock system verification, and consists of one or two SPDT switches housed in a plug-in module. Each SPDT switch has one "a" and one "b" contact. When the circuit breaker contacts are open, the "a" contact is open and the "b" contact is closed.

Auxiliary Switch and Alarm Switch Combination

Each catalog number listed in tables on **Pages V4-T2-278** and **V4-T2-279** includes one auxiliary switch and one alarm switch. In an auxiliary switch ASL switch combination, the auxiliary switch is always mounted on the side of the plug-in module next to the center pole of the circuit breaker.

Shunt Trip

The shunt trip provides remote controlled tripping of the circuit breaker. The shunt trip consists of an intermittent rated solenoid with a tripping plunger and a cutoff switch assembled to a plug-in module. When required for ground fault protection applications, certain AC rated shunt trips, as noted in the electrical rating table, are suitable for operation at 55 percent of rated voltage.

Select shunt trip catalog number for the voltage within the indicated voltage range. Shunt trip coils are designed to be applied at specific AC or DC voltages within the voltage range shown. Electrical ratings are also shown on applicable circuit breaker accessory nameplates.

Low Energy Shunt Trip

Low energy shunt trip devices are designed to operate from low energy output signals from dedicated current sensors typically applied in ground fault protection schemes. However, with a proper control voltage source, they may be applied in place of conventional trip devices for special applications. Flux paths surrounding permanent magnets used in the shunt trip assembly hold a charged spring poised in readiness to operate the circuit breaker trip mechanism.

When a 100 microfarad capacitor charged to 28 Vdc is discharged through the shunt trip coil, the resultant flux opposes the permanent magnet flux field, which releases the stored energy in the spring to trip the circuit breaker. As the circuit breaker resets, the shunt trip reset arm is actuated by the circuit breaker handle, resetting the shunt trip. The plug-in module is mounted in retaining slots in the top of the trip unit. Coil is intermittent-rated only. Cutoff provisions required in control circuit.

Undervoltage Release Mechanism

The undervoltage release mechanism monitors a voltage (typically a line voltage) and trips the circuit breaker when the voltage falls to between 70 and 35 percent of the solenoid coil rating.

The undervoltage release mechanism consists of a continuous rated solenoid with a plunger and tripping lever mounted in a plug-in module. The tab on the tripping lever resets the undervoltage release mechanism when normal voltage has been restored and the circuit breaker handle is moved to the reset (or OFF) position. With less than pickup voltage applied to the undervoltage release mechanism, the circuit breaker contacts will not touch when a closing operation is attempted.

Note: Undervoltage release mechanism accessories are not designed for, and should not be used as, circuit interlocks.

Accessory Terminal Block (R-Frame)

(For fixed-mounted configuration.)

Internal accessory wiring leads are normally supplied with pigtail leads (18 AWG) that exit from the right side of the circuit breaker. Where specified, fixed-mounted accessory terminal blocks are available. A maximum of one 24-point terminal block can be installed on the right side of the circuit breaker for the internal accessories.

For convenience in determining the appropriate number of terminal block points required, refer to **Page V4-T2-274**.

PowerNet and Zone Interlock Kits (OPTIM 550 only) K-, L- and N-Frames

Eaton's PowerNet Communications Kit can be ordered to add PowerNet communications to an existing OPTIM 550 breaker in the field. An 18-inch (457.2 mm) wiring pigtail is routed to the rear of the breaker: two wires for PowerNet and two wires for 24 Vdc (45 mA load). It is recommended that the power supply be an "isolated high quality" unit.

Product Selection

Alarm Switch

Alarm Switch



G-Frame Alarm Switch (RH Only) ①

Electrical Ratings			Contact Arrangement	Factory Suffix	Catalog Number ②③④
Volts	Frequency	Amperes			
Alarm Switch					
240	50/60 Hz	6	1 Make/1 Break	**B3**	**1288C75G03**
Alarm Switch Auxiliary Switches Combination					
240	50/60 Hz	6	1 Make/1 Break and 1A/1B	**B13**	**1288C76G09**

F-Frame Alarm Switch ①

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Factory Installation Kit ⑤	
Number of Contacts (Make and Break)	Mounting Location (Pole)	Same Side Suffix Number	Rear ⑥ Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left ⑦	**B01**	**B02**	**B03**	**B04**	**A1L1LPK**	**A1L1LTK**
	Right	**B05**	**B06**	**B07**	**B08**	**A1L1RPK**	**A1L1RTK**
2	Left ⑦	**B09**	**B10**	—	**B11**	**A2L1LPK**	**A2L1LTK**
	Right	**B12**	**B13**	—	**B14**	**A2L1RPK**	**A2L1RTK**
1	Single-pole	**B15** ⑧	—	—	—	—	—

F-Frame HMCP Alarm Switch ①

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Factory Installation Kit ⑤	
Number of Contacts (Make and Break)	Mounting Location (Pole)	Same Side Suffix Number	Rear ⑥ Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left ⑦	**B01**	**B02**	**B03**	**B04**	**MA1L1LPK**	**MA1L1LTK**
	Right	**B05**	**B06**	**B07**	**B08**	**MA1L1RPK**	**MA1L1RTK**
2	Left ⑦	**B09**	**B10**	—	**B11**	**MA2L1LPK**	**MA2L1LTK**
	Right	**B12**	**B13**	—	**B14**	**MA2L1RPK**	**MA2L1RTK**

J-Frame and HMCP (J) Alarm Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Field Installation Kits ⑨	
Number of Contacts (Make and Break)	Mounting Location (Pole)	Same Side Suffix Number	Rear ⑦ Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left ⑩	**B01**	**B02**	**B03**	**B04**	**A1L2LPK**	**A1L2LTK**
	Right	**B05**	**B06**	**B07**	**B08**	**A1L2RPK**	**A1L2RTK** ⑥

Notes

① F-Frame circuit breakers are factory sealed. Underwriters Laboratories requires that internal accessories be installed at the factory. Internal accessories are UL listed for factory installation under E7819. Where local codes and standards permit and UL listing is not required, internal accessories can be field installed; however, this is not recommended for FDE breakers. Accessory installation should be done before the circuit breaker is mounted and connected.

② Includes 24-inch (609.6 mm) external pigtail leads,18 AWG (16–0.010).

③ A maximum of two internal accessories may be mounted in a three-pole circuit breaker.

④ Suitable for mounting in right pole only of two- or three-pole breaker.

⑤ Not listed with Underwriters Laboratories; for field installation.

⑥ Standard pigtail lead exit location.

⑦ Standard mounting location.

⑧ Factory installation only. Leads exit load end of circuit breaker.

⑨ Listed with Underwriters Laboratories; for field installation on interchangeable trip unit breakers under E64983.

⑩ Standard mounting location—leads exit rear of breaker.

K-Frame and HMCP (K) Alarm Switch

Number of Sets of Contacts (1M and 1B)	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left ③	B01	B02	B03	B04	A1L3LPK	A1L3LTK
	Right ④	B05	B06	B07	B08	A1L3RPK	A1L3RTK
2	Left ③	B09	B10	—	B11	A2L3LPK	A2L3LTK
	Right ④	B12	B13	—	B14	A2L3RPK	A2L3RTK

L-, HMCP (L) and (M) Frames and Alarm Switch

Number of Sets of Contacts (1M and 1B)	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left ③	B01	B02	B03	B04	A1L4LPK	A1L4LTK
	Right	B05	B06	B07	B08	A1L4RPK	A1L4RTK
2	Left ③	B09	B10	—	B11	A2L4LPK	A2L4LTK
	Right	B12	B13	—	B14	A2L4RPK	A2L4RTK

N-Frame and HMCP (N) Alarm Switch

Number of Sets of Contacts (1M and 1B)	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ⑤ Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left	B01	B02	B03	B04	A1L5LPK	A1L5LTK
	Right ③	B05	B06	B07	B08	A1L5RPK	A1L5RTK
2	Left	B09	B10	—	B11	A2L5LPK	A2L5LTK
	Right ③	B12	B13	—	B14	A2L5RPK	A2L5RTK

R-Frame Alarm Switch (RH Only)

Number of Contacts (Make and Break)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Suffix Number ⑥	Field Mounted Field Installation Kits ⑤ Pigtail Leads Catalog Number ⑥
1	B05	A1L6RPK
2	B12	A2L6RPK

Notes

① Listed with Underwriters Laboratories; for field installation on interchangeable trip unit breakers under E64983.
② Standard mounting location.
③ Standard mounting location—leads exit rear of breaker.
④ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.
⑤ Listed with Underwriters Laboratories for field installation under E64983.
⑥ A maximum of three ASL plug-in modules may be installed in a circuit breaker.

Auxiliary Switch

Auxiliary Switch



G-Frame Auxiliary Switch (RH Only)

Electrical Ratings Volts	Frequency	Amperes	Contact Arrangement	Factory Suffix	Catalog Number ①②
240	50/60 Hz	6	1a/1b	**A3**	**1288C74G03**
240	50/60 Hz	6	2a/2b	**A6**	**1288C73G03**

F-Frame and HMCP (F) Auxiliary Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Factory Installation Kit ④	
					Terminal Block	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Same Side Suffix Number	Rear ③ Suffix Number	Opposite Side Suffix Number	Same Side Suffix Number	Catalog Number	Catalog Number
1	Left ⑤	**A01**	**A02**	**A03**	**A04**	**A1X1PK**	**A1X1LTK**
	Left ⑤	**A15** ⑦	**A16** ⑦	**A17** ⑦	—	**E1X1PK**	—
	Right or Neutral ⑥	**A05**	**A06**	**A07**	**A08**	**A1X1PK**	**A1X1RTK** ⑧
	Right or Neutral ⑥	**A18** ⑦	**A19** ⑦	**A20** ⑦	—	—	—
2	Left ⑤	**A09**	**A10**	—	**A11**	**A2X1LPK**	**A2X1LTK**
	Left ⑤	**A21** ⑦	**A22** ⑦	—	—	**E2X1LPK**	—
	Right or Neutral ⑥	**A12**	**A13**	—	**A14**	**A2X1RPK**	**A2X1RTK** ⑧
	Right or Neutral ⑥	**A23** ⑦	**A24** ⑦	—	—	**E2X1RPK**	—

F-Frame with Electronic Trip Unit Auxiliary Switch ⑨

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Factory Installation Kit ④	
					Terminal Block	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Same Side Suffix Number	Rear Suffix Number	Opposite Side Suffix Number	Same Side Suffix Number	Catalog Number	Catalog Number
Trip Unit Type 310+							
1	Right	**A30**	**A31**	**A32**	—	—	—
Trip Unit Type 210+							
1	Right	**A33**	**A34**	**A35**	—	—	—

J-Frame and HMCP (J) Auxiliary Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Factory Installation Kit ⑩	
					Terminal Block	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Same Side Suffix Number	Rear ③ Suffix Number	Opposite Side Suffix Number	Same Side Suffix Number	Catalog Number	Catalog Number
1	Left	**A01**	**A02**	**A03**	**A04**	**A1X2PK**	**A1X2LTK**
	Right ⑪	**A05**	**A06**	**A07**	**A08**	**A1X2PK**	**A1X2RTK** ④
2	Left	**A09**	**A10**	—	**A11**	**A2X2PK**	**A2X2LTK**
	Right ⑪	**A12**	**A13**	—	**A14**	**A2X2PK**	**A2X2RTK** ④

Notes

① Includes 24-inch external pigtail leads, 18 AWG (16–0.010).
② A maximum of two internal accessories may be mounted in a three-pole circuit breaker. Suitable for mounting in right pole only of two- or three-pole breaker.
③ Standard pigtail lead exit location.
④ Not listed with Underwriters Laboratories; for field installation.
⑤ Pigtail wire size: 18 AWG (0.82 mm^2).
⑥ Not for use on F-Frame with electronic trip unit.
⑦ 125 volts (max.), 50/60 Hz switch for use in electronic circuit of 100 micro amperes and 15 Vdc minimum.
⑧ Not for use on four-pole circuit breakers.
⑨ Only for use on three-pole F-Frame breakers with electronic trip unit. Installation auxiliary switch for FD electronic breakers on right pole must be performed at breaker factory.
⑩ Listed with Underwriters Laboratories for field installation or interchangeable trip unit breakers under E64983.
⑪ Standard mounting location—leads exit rear of breaker.

K-Frame and HMCP (K) Auxiliary Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Factory Installation Kit ①	
		Same Side	Rear ②	Opposite Side	Terminal Block Same Side	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
1	Left	A01	A02	A03	A04	A1X3PK	A1X3LTK
	Right ②③	A05	A06	A07	A08	A1X3PK	A1X3RTK ④
2	Left	A09	A10	—	A11	A2X3PK	A2X3LTK
	Right ②③	A12	A13	—	A14	A2X3PK	A2X3RTK ④
	Right	A21	A22	—	—	1482D28G10 ⑥⑦	—
3	Left	A18	—	—	A15	A3X3LPK	A3X3LTK
	Right ③	A17	—	—	A16	A3X3RPK	A3X3RTK ④

L-, HMCP (L) and (M) Frames and Auxiliary Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Factory Installation Kit ①	
		Same Side	Rear ②	Opposite Side	Terminal Block Same Side	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
1	Left	A01	A02	A03	A04	A1X4PK	A1X4LTK
	Right ②	A05	A06	A07	A08	A1X4PK	A1X4RTK ④
2	Left	A09	A10	—	A11	A2X4PK	A2X4LTK
	Right ②	A12	A13	—	A14	A2X4PK	A2X4RTK ④
3	Left	A18	—	—	A15	A3X4PK	A3X4LTK
	Right ②	A17	—	—	A16	A3X4PK	A3X4RTK ④

N-Frame and HMCP (N) Auxiliary Switch

		Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Factory Installation Kit ①	
		Same Side	Rear ②	Opposite Side	Terminal Block Same Side	Pigtail Leads	Terminal Block
Number of Contacts A and B	Mounting Location (Pole)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
1	Left	A01	A02	A03	A04	A1X5PK	A1X5LTK
	Right ②	A05	A06	A07	A08	A1X5PK	A1X5RTK ④
2	Left	A09	A10	—	A11	A2X5PK	A2X5LTK
	Right ②	A12	A13	—	A14	A2X5PK	A2X5RTK ④
3	Left	A18	—	—	A15	A3X5LPK	A3X5LTK
	Right ②	A17	—	—	A16	A3X5RPK	A3X5RTK ④

R-Frame Auxiliary Switch (RH Only)

	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads	Field Mounted Field Installation Kits ① Pigtail Leads
Number of Contacts A and B	Suffix Number ⑤	Catalog Number ⑤
2	A12	A2X6RPK
4	A19	A4X6RPK

Notes

① Listed with Underwriters Laboratories for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.
④ Not for use on four-pole circuit breakers.
⑤ A maximum of two auxiliary switches (any combination of 2a/2b or 4a/4b plug-in modules may be installed in a circuit breaker.
⑥ This option is not field installable.
⑦ Available on the OPTIM 550 only. Communications are not available with this option.

Auxiliary Switch and Alarm Switch Combination

Auxiliary Switch and Alarm Switch Combination



F-Frame Auxiliary Switch and Alarm Switch Combination ①

Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ③ Suffix Number	Terminal Block Same Side Suffix Number	Factory Installation Kit ② Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left ③	C01	C02	C03	AAL1LPK	AAL1LTK
Right	C04	C05	C06	AAL1RPK	AAL1RTK ④

F-Frame HMCP Auxiliary Switch and Alarm Switch Combination

Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ③ Suffix Number	Terminal Block Same Side Suffix Number	Factory Installation Kit ② Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left ④	C01	C02	C03	MAAL1LPK	MAAL1LTK
Right	C04	C05	C06	MAAL1RPK	MAAL1RPK

J-Frame and HMCP (J) Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts (1A and 1B) (1M–1B)	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ⑥ Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ⑤ Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left	C01	C02	—	C03	AAL2LPK	AAL2LTK
	Right ④	C04	C05	—	C06	AAL2RPK	AAL2RTK ④

K-Frame and HMCP (K) Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts (1A and 1B) (1M–1B)	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ⑥ Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ⑤ Pigtail Leads Catalog Number	Terminal Block Catalog Number
1	Left	C01	C02	—	C03	AAL3LPK	AAL3LTK
	Right ⑥⑦	C04	C05	—	C06	AAL3RPK ⑧	AAL3RTK
	Right	C07	C08	—	—	1482D28G09 ⑨⑩	—

Notes

① Auxiliary switch and alarm switch combination options (Cxx) are not available on FDE 310+ with LSG or LSIG trip units due to exit wire limitations. To obtain both features, order a left mounting alarm switch (B01-B04 or B09-B11), and right mounting auxiliary switch (A30-A32).
② Not listed with Underwriters Laboratories for field installation.
③ Standard mounting location.
④ Not for use on four-pole circuit breakers
⑤ Listed with Underwriters Laboratories for field installation of interchangeable trip unit breakers under E64983.
⑥ Standard mounting location—leads exit rear of breaker.
⑦ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.
⑧ Will not install on OPTIM Trip (RH).
⑨ Available on the OPTIM 550 only. Communications are not available with this option.
⑩ This option is not field installable.

L-, HMCP (L) and (M) Frames and Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
1A, 1B and 1 Make/1 Break	Left	C01	C02	—	C03	AA114LPK	AA114LTK
	Right ②	C04	C05	—	C06	AA114RPK	AA114RTK ③
2A, 2B and 1 Make/1 Break	Left	C07	C08	—	C12	AA214LPK	AA214LTK
	Right ②	C10	C11	—	C13	AA214RPK	AA214RTK ③
3A, 3B and 1 Make/1 Break	Left	C14	—	—	—	AA314LPK	—
	Right ②	C15	—	—	—	AA314RPK	—

N-Frame and HMCP (N) Auxiliary Switch and Alarm Switch Combination

Number of Sets of Contacts	Mounting Location (Pole)	Factory Mounted Connection Type and Location 18-Inch (457 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
1A, 1B and 1 Make/1 Break	Left	C01	C02	—	C03	AA115LPK	AA115LTK
	Right ②	C04	C05	—	C06	AA115RPK	AA115RTK ③
2A, 2B and 1 Make/1 Break	Left	C07	C08	—	C12	AA215LPK	AA215LTK
	Right ②	C10	C11	—	C13	AA215RPK	AA215RTK ③

Notes

① Listed with Underwriters Laboratories for field installation under E64983.

② Standard mounting location—leads exit rear of breaker.

③ Not for use on four-pole circuit breaker.

Shunt Trip

Shunt Trip



G-Frame Shunt Trip (LH Three-Pole Only)

Electrical Ratings				
Volts	**Frequency**	**Amperes**	**Suffix Number**	**Catalog Number**
120	50/60 Hz	1.1	**S1**	**1373D62G01**
240	50/60 Hz	2.1	**S2**	**1373D62G02**
12	DC	2.8	**S3**	**1373D62G15**
24	DC	5.7	**S4**	**1373D62G16**
24	60 Hz	—	**S7**	**1373D62G20**

F-Frame and HMCP (F) Shunt Trip

	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads ②				Factory Installation Kit ①	
	Same Side	**Rear ③**	**Opposite Side**	**Terminal Block Same Side**	**Pigtail Leads**	**Terminal Block**
Voltage Rating (AC Frequency = 50/60 Hz)	**Suffix Number**	**Suffix Number**	**Suffix Number**	**Suffix Number**	**Catalog Number**	**Catalog Number**
Left-Pole Mounting AC/DC Ratings						
12–24 Vac or Vdc	**S01**	**S02**	**S03**	**S04**	**SNT1LP03K**	**SNT1LT03K**
48–127 Vac or 48–60 Vdc ④	**S05**	**S06**	**S07**	**S08**	**SNT1LP08K**	**SNT1LT08K**
208–380 Vac or 110–127 Vdc	**S09**	**S10**	**S11**	**S12**	**SNT1LP12K**	**SNT1LT12K**
415–600 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT1LP18K**	**SNT1LT18K**
Right- or Neutral-Pole Mounting AC/DC Ratings ⑤						
12–24 Vac or Vdc	**S17**	**S18**	**S19**	**S20**	**SNT1RP03K**	**SNT1RT03K ⑥**
48–127 Vac or 48–60 Vdc ④	**S21**	**S22**	**S23**	**S24**	**SNT1RP08K**	**SNT1RT08K ⑥**
208–380 Vac or 110–127 Vdc	**S25**	**S26**	**S27**	**S28**	**SNT1RP12K**	**SNT1RT12K ⑥**
415–600 Vac or 220–250 Vdc	**S29**	**S30**	**S31**	**S32**	**SNT1RP18K**	**SNT1RT18K ⑥**

Notes

① Not listed with Underwriters Laboratories, for field installation.
② Pigtail wire size: 18 AWG (0.82 mm^2).
③ Standard pigtail lead exit location.
④ 120 Vac marked suitable for ground fault protection devices.
⑤ Standard mounting location.
⑥ Not for use on four-pole circuit breakers.

G-Frame circuit breakers are factory sealed. Underwriters Laboratories requires that internal accessories be installed at the factory.

Internal accessories are UL listed for factory installation under E7819.

Where local codes and standards permit and UL listing is not required, internal accessories can be field installed.
Accessory installation should be done before the circuit breaker is mounted and connected.

J-Frame and HMCP (J) Shunt Trip

Voltage Rating (AC Frequency = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left-Pole Mounting AC/DC Ratings ②						
12–24 Vac or Vdc	**S41**	**S42**	**S43**	**S44**	**SNT2P04K**	**SNT2T04K**
48–60 Vac or Vdc	**S49**	**S50**	**S51**	**S52**	**SNT2P06K**	**SNT2T06K**
110–240 Vac or 110–125 Vdc ③	**S09**	**S10**	**S11**	**S12**	**SNT2P11K**	**SNT2T11K**
380–440 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT2P14K**	**SNT2T14K**
480–600 Vac	**S17**	**S18**	**S19**	**S20**	**SNT2P18K**	**SNT2T18K**
Right- or Neutral-Pole Mounting AC/DC Ratings						
12–24 Vac or Vdc	**S45**	**S46**	**S47**	**S48**	**SNT2P04K**	**SNT2T04K** ④
48–60 Vac or Vdc	**S53**	**S54**	**S55**	**S56**	**SNT2P06K**	**SNT2T06K** ④
110–240 Vac or 110–125 Vdc ③	**S29**	**S30**	**S31**	**S32**	**SNT2P11K**	**SNT2T11K** ④
380–440 Vac or 220–250 Vdc	**S33**	**S34**	**S35**	**S36**	**SNT2P14K**	**SNT2T14K** ④
480–600 Vac	**S37**	**S38**	**S39**	**S40**	**SNT2P18K**	**SNT2T18K** ④

K-Frame and HMCP (K) Shunt Trip

Voltage Rating (AC Frequency = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left-Pole Mounting AC/DC Ratings ②						
12–24 Vac or Vdc	**S41**	**S42**	**S43**	**S44**	**SNT3P04K**	**SNT3T04K**
48–60 Vac or Vdc	**S49**	**S50**	**S51**	**S52**	**SNT3P06K**	**SNT3T06K**
110–240 Vac or 110–125 Vdc ③	**S09**	**S10**	**S11**	**S12**	**SNT3P11K**	**SNT3T11K**
380–440 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT3P14K**	**SNT3T14K**
480–600 Vac	**S17**	**S18**	**S19**	**S20**	**SNT3P18K**	**SNT3T18K**
Right- or Neutral-Pole Mounting AC/DC Ratings ⑤⑥						
12–24 Vac or Vdc	**S45**	**S46**	**S47**	**S48**	**SNT3P04K**	**SNT3T04K** ④
48–60 Vac or Vdc	**S53**	**S54**	**S55**	**S56**	**SNT3P06K**	**SNT3T06K** ④
110–240 Vac or 110–125 Vdc ③	**S29**	**S30**	**S31**	**S32**	**SNT3P11K**	**SNT3T11K** ④
380–440 Vac or 220–250 Vdc	**S33**	**S34**	**S35**	**S36**	**SNT3P14K**	**SNT3T14K** ④
480–600 Vac	**S37**	**S38**	**S39**	**S40**	**SNT3P18K**	**SNT3T18K** ④

Notes

① Listed with Underwriters Laboratories for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ Suitable for use with Class 1 ground fault sensing element.
④ Not for use on four-pole circuit breakers.
⑤ For use with KT (thermal-magnetic) trip units only.
⑥ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.

L-, HMCP (L) and (M) Frames and Shunt Trip

	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Field Installation Kits ①	
	Same Side	Rear ②	Opposite Side	Terminal Block Same Side	Pigtail Leads	Terminal Block
Voltage Rating (AC Frequency = 50/60 Hz)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
Left-Pole Mounting AC/DC Ratings ②						
12–24 Vac or Vdc	**S01**	**S02**	**S03**	**S04**	**SNT4LP03K**	**SNT4LT03K**
48–60 Vac	**S05**	**S06**	**S07**	**S08**	**SNT4LP05K**	**SNT4LT05K**
48–60 Vdc	**S85**	**S86**	**S87**	—	**SNT4LP23K**	**SNT4LT23K**
110–240 Vac	**S09**	**S10**	**S11**	**S12**	**SNT4LP11K**	**SNT4LT11K**
110–125 Vdc	**S41**	**S42**	**S43**	**S44**	**SNT4LP26K**	**SNT4LT26K**
380–440 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT4LP14K**	**SNT4LT14K**
480–600 Vac	**S17**	**S18**	**S19**	**S20**	**SNT4LP18K**	**SNT4LT18K**
Right-Pole Mounting AC/DC Ratings ③						
12–24 Vac or Vdc	**S21**	**S22**	**S23**	**S24**	**SNT4RP03K**	**SNT4RT03K**
48–60 Vac	**S25**	**S26**	**S27**	**S28**	**SNT4RP05K**	**SNT4RT05K**
48–60 Vdc	**S88**	**S89**	**S90**	—	**SNT4RP23K**	**SNT4RT23K**
110–240 Vac	**S29**	**S30**	**S31**	**S32**	**SNT4RP11K**	**SNT4RT11K**
110–125 Vdc	**S45**	**S46**	**S47**	**S48**	**SNT4RP26K**	**SNT4RT26K**
380–440 Vac or 220–250 Vdc	**S33**	**S34**	**S35**	**S36**	**SNT4RP14K**	**SNT4RT14K**
480–600 Vac	**S37**	**S38**	**S39**	**S40**	**SNT4RP18K**	**SNT4RT18K**

Notes

① Listed with Underwriters Laboratories, for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ For use with LT (thermal-magnetic) three-pole trip units only.

N-Frame and HMCP (N) Shunt Trip

Voltage Rating (AC Frequency = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left-Pole Mounting AC/DC Ratings ②						
9–24 Vac or Vdc	**S01**	**S02**	**S03**	**S04**	**SNT5LP03K**	**SNT5LT03K**
48–60 Vac	**S05**	**S06**	**S07**	**S08**	**SNT5LP05K**	**SNT5LT05K**
110–240 Vac ③	**S09**	**S10**	**S11**	**S12**	**SNT5LP11K**	**SNT5LT11K**
110–125 Vdc	**S41**	**S42**	**S43**	**S44**	**SNT5LP26K**	**SNT5LT26K**
380–440 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT5LP14K**	**SNT5LT14K**
480–600 Vac	**S17**	**S18**	**S19**	**S20**	**SNT5LP18K**	**SNT5LT18K**
48–60 Vdc	**S21**	**S22**	**S23**	**S24**	**SNT5LP23K**	**SNT5LT23K**

R-Frame Shunt Trip (RH Only)

Voltage Rating (AC Frequency = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Suffix Number ④	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number ④
24 Vac or Vdc	**S21**	**SNT6P03K**
48–60 Vac	**S25**	**SNT6P05K**
110–240 Vac	**S29**	**SNT6P11K**
380–440 Vac or 220–250 Vdc	**S33**	**SNT6P14K**
480–600 Vac	**S37**	**SNT6P18K**
48–60 Vdc	**S88**	**SNT6P23K**
110–125 Vdc	**S45**	**SNT6P26K**

Notes

① Listed with Underwriters Laboratories for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ Supply voltages suitable for use with Class 1 GFP devices. Marking label included with accessory kits.
④ A maximum of two shunt trip plug-in modules may be installed in a circuit breaker.

Low Energy Shunt Trip
Ordering Information

Select shunt trip catalog number for the voltage within the indicated voltage range. Shunt trip coils are designed to be applied at specific AC or DC voltages within the voltage range shown. Electrical ratings are also shown on applicable circuit breaker accessory nameplates.

Low Energy Shunt Trip



F-, J-, K-, L-, M-, N- and R-Frames and HMCPs Low Energy Shunt Trip ①

	Factory Mounted			Field Mounted		
	Connection Type and Location			Field Installation Kits ②		
	18-Inch (457.2 mm) Pigtail Leads			Terminal Block		
Mounting Positions (Pole)	Same Side Suffix Number	Rear ③ Suffix Number	Opposite Side Suffix Number	Same Side Suffix Number	Pigtail Leads Catalog Number	Terminal Block Catalog Number
F-Frame						
Left	**N01**	**N02**	**N03**	**N04**	**LST1LPK** ④	**LST1LTK** ④
Right ③	**N05**	**N06**	**N07**	**N08**	**LST1RPK** ④	**LST1RTK** ④
J-Frame						
Left	**N01**	**N02**	**N03**	—	**LST2LPK**	—
Right ③	**N05**	**N06**	**N07**	—	**LST2RPK**	—
K-Frame						
Left ③	**N01**	**N02**	**N03**	—	**LST3LPK**	—
Right ⑤⑥	**N05**	**N06**	**N07**	—	**LST3RPK**	—
L- and M-Frames						
Left	**N01**	**N02**	**N03**	—	**LST4LPK**	—
Right	**N05**	**N06**	**N07**	—	**LST4RPK**	—
N-Frame						
Left ③	**N01**	**N02**	**N03**	—	**LST5LPK**	—
R-Frame						
Right	**N01**	—	—	—	**LST6RPK**	—

Notes

① Cutoff provisions required in control circuit.
② Listed with Underwriters Laboratories for field installation under E64983.
③ Standard mounting location—leads exit rear of breaker.
④ For F-Frame HMCP, add an "M" to beginning of catalog number. Field Installation Kit referenced for factory use only, not UL listed for field installation.
⑤ For use with thermal-magnetic trip units only.
⑥ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.

Undervoltage Release Mechanism

Ordering Information

2

Select handle reset undervoltage release mechanism catalog number for the voltage within the indicated voltage range. Undervoltage release mechanism coils are designed to be applied at specific AC or DC voltages within the voltage range shown on applicable circuit breaker accessory nameplates.

Undervoltage Release Mechanism



G-Frame Undervoltage Release Mechanism (LH Three-Pole Only)

Electrical Ratings Volts (AC Only)	Frequency (Hz)	Amperes	Style Numbers ①②③	Factory Suffix
120	50/60	0.05	**1373D62G03**	**T1**
24	50/60	0.22	**1373D62G04**	**T2**
48	50/60	0.11	**1373D62G05**	**T3**
60	50/60	0.10	**1373D62G06**	**T4**
110	50	0.049	**1373D62G07**	**T5**
208	60	0.026	**1373D62G08**	**T6**
220	50	0.025	**1373D62G09**	**T7**
240	50/60	0.024	**1373D62G10**	**T8**
380	50	0.015	**1373D62G11**	**T9**
415	50	0.013	**1373D62G12**	**T10**
440	50	0.012	**1373D62G13**	**T11**
480	60	0.01	**1373D62G14**	**T12**

Notes

① Includes 24-inch (609.6 mm) external pigtail leads, 18 AWG (16–0.010).

② A maximum of two internal accessories may be mounted in a three-pole circuit breaker.

③ Suitable for mounting in left pole only of three-pole breaker.

G-Frame circuit breakers are factory sealed. Underwriters Laboratories requires that internal accessories be installed at the factory.

Internal accessories are UL listed for factory installation under E7819.

Where local codes and standards permit and UL listing is not required, internal accessories can be field installed. Accessory installation should be done before the circuit breaker is mounted and connected.

F-Frame Factory Mounted (For F-Frame Breaker and F-Frame HMCP) Undervoltage Release Mechanism

Voltage Rating (AC Freq. = 50/60 Hz)	Connection Type and Location: 18-Inch Pigtail Leads, Same Side Suffix Number	18-Inch Pigtail Leads, Rear ① Suffix Number	Opposite Side Suffix Number	Terminal Block, Same Side Suffix Number
Left-Pole Mounting AC Ratings				
12 Vac	**U01**	**U02**	**U03**	**U04**
24 Vac	**U05**	**U06**	**U07**	**U08**
48 Vac	**U37**	**U38**	**U39**	**U40**
60 Vac	**U97**	**U98**	**U99**	**U100**
110–127 Vac	**U13**	**U14**	**U15**	**U16**
208–240 Vac	**U17**	**U18**	**U19**	**U20**
380–480 Vac	**U21**	**U22**	**U23**	**U24**
525–600 Vac	**U25**	**U26**	**U27**	**U28**
Right-Pole Mounting AC Ratings ②③				
12 Vac	**U49**	**U50**	**U51**	**U52**
24 Vac	**U53**	**U54**	**U55**	**U56**
48 Vac	**U85**	**U86**	**U87**	**U88**
60 Vac	**U101**	**U102**	**U103**	**U104**
110–127 Vac	**U61**	**U62**	**U63**	**U64**
208–240 Vac	**U65**	**U66**	**U67**	**U68**
380–480 Vac	**U69**	**U70**	**U71**	**U72**
525–600 Vac	**U73**	**U74**	**U75**	**U76**
Left-Pole Mounting DC Ratings				
12 Vdc	**U29**	**U30**	**U31**	**U32**
24 Vdc	**U33**	**U34**	**U35**	**U36**
48 Vdc	**U37**	**U38**	**U39**	**U40**
60 Vdc	**U97**	**U98**	**U99**	**U100**
110–127 Vdc	**U41**	**U42**	**U43**	**U44**
220–250 Vdc	**U45**	**U46**	**U47**	**U48**
Right-Pole Mounting DC Ratings ②③				
12 Vdc	**U77**	**U78**	**U79**	**U80**
24 Vdc	**U81**	**U82**	**U83**	**U84**
48 Vdc	**U85**	**U86**	**U87**	**U88**
60 Vdc	**U101**	**U102**	**U103**	**U104**
110–127 Vdc	**U89**	**U90**	**U91**	**U92**
220–250 Vdc	**U93**	**U94**	**U95**	**U96**

Notes

① Standard pigtail lead exit location.

② Standard mounting location.

③ Not for use on right pole of four-pole circuit breaker.

F-Frame circuit breakers are factory sealed. Underwriters Laboratories requires that internal accessories be installed at the factory.

Internal accessories are UL listed for factory installation under E7819.

Where local codes and standards permit and UL listing is not required, internal accessories can be field installed. Accessory installation should be done before the circuit breaker is mounted and connected.

2

F-Frame Field Mounted Undervoltage Release Mechanism

Voltage Rating (AC Freq. = 50/60 Hz)	F-Frame Breaker Factory Installation Kits ① Pigtail Leads Catalog Number	F-Frame Breaker Factory Installation Kits ① Terminal Block Catalog Number	F-Frame Breaker HMCP Pigtail Leads Catalog Number	F-Frame Breaker HMCP Terminal Block Catalog Number
Left-Pole Mounting AC Ratings				
12 Vac	**UVH1LP02K**	**UVH1LT02K**	**MUVH1LP02K**	**MUVH1LT02K**
24 Vac	**UVH1LP03K**	**UVH1LT03K**	**MUVH1LP03K**	**MUVH1LT03K**
48 Vac	**UVH1LP22K**	**UVH1LT22K**	**MUVH1LP22K**	**MUVH1LT22K**
60 Vac	**UVH1LP24K**	**UVH1LT24K**	**MUVH1LP24K**	**MUVH1LT24K**
110–127 Vac	**UVH1LP08K**	**UVH1LT08K**	**MUVH1LP08K**	**MUVH1LT08K**
208–240 Vac	**UVH1LP11K**	**UVH1LT11K**	**MUVH1LP11K**	**MUVH1LT11K**
380–480 Vac	**UVH1LP15K**	**UVH1LT15K**	**MUVH1LP15K**	**MUVH1LT15K**
525–600 Vac	**UVH1LP18K**	**UVH1LT18K**	**MUVH1LP18K**	**MUVH1LT18K**
Right-Pole Mounting AC Ratings ②③				
12 Vac	**UVH1RP02K**	**UVH1RT02K**	**MUVH1RP02K**	**MUVH1RT02K**
24 Vac	**UVH1RP03K**	**UVH1RT03K**	**MUVH1RP03K**	**MUVH1RT03K**
48 Vac	**UVH1RP22K**	**UVH1RT22K**	**MUVH1RP22K**	**MUVH1RT22K**
60 Vac	**UVH1RP24K**	**UVH1RT24K**	**MUVH1RP24K**	**MUVH1RT24K**
110–127 Vac	**UVH1RP08K**	**UVH1RT08K**	**MUVH1RP08K**	**MUVH1RT08K**
208–240 Vac	**UVH1RP11K**	**UVH1RT11K**	**MUVH1RP11K**	**MUVH1RT11K**
380–480 Vac	**UVH1RP15K**	**UVH1RT15K**	**MUVH1RP15K**	**MUVH1RT15K**
525–600 Vac	**UVH1RP18K**	**UVH1RT18K**	**MUVH1RP18K**	**MUVH1RT18K**
Left-Pole Mounting DC Ratings				
12 Vdc	**UVH1LP20K**	**UVH1LT20K**	**MUVH1LP20K**	**MUVH1LT20K**
24 Vdc	**UVH1LP21K**	**UVH1LT21K**	**MUVH1LP21K**	**MUVH1LT21K**
48 Vdc	**UVH1LP22K**	**UVH1LT22K**	**MUVH1LP22K**	**MUVH1LT22K**
60 Vdc	**UVH1LP24K**	**UVH1LT24K**	**MUVH1LP24K**	**MUVH1LT24K**
110–127 Vdc	**UVH1LP26K**	**UVH1LT26K**	**MUVH1LP26K**	**MUVH1LT26K**
220–250 Vdc	**UVH1LP28K**	**UVH1LT28K**	**MUVH1LP28K**	**MUVH1LT28K**
Right-Pole Mounting DC Ratings ②③				
12 Vdc	**UVH1RP20K**	**UVH1RT20K**	**MUVH1RP20K**	**MUVH1RT20K**
24 Vdc	**UVH1RP21K**	**UVH1RT21K**	**MUVH1RP21K**	**MUVH1RT21K**
48 Vdc	**UVH1RP22K**	**UVH1RT22K**	**MUVH1RP22K**	**MUVH1RT22K**
60 Vdc	**UVH1RP22K**	**UVH1RT22K**	**MUVH1RP22K**	**MUVH1RT22K**
110–127 Vdc	**UVH1RP26K**	**UVH1RT26K**	**MUVH1RP26K**	**MUVH1RT26K**
220–250 Vdc	**UVH1RP28K**	**UVH1RT28K**	**MUVH1RP28K**	**MUVH1RT28K**

Notes

① Not listed with Underwriters Laboratories, for field installation.
② Standard mounting location.
③ Not for use on right pole of four-pole circuit breaker.

J-Frame and HMCP (J) Undervoltage Release Mechanism

	Factory Mounted Connection Type and Location				Field Mounted Field Installation Kits ②	
	18-Inch (457.2 mm) Pigtail Leads			Terminal Block ①		
	Same Side	Rear ②	Opposite Side	Same Side	Pigtail Leads	Terminal Block ③
Voltage Rating (AC Freq. = 50/60 Hz)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
Left-Pole Mounting AC Ratings ④						
12 Vac	**U05**	**U06**	**U07**	**U08**	**UVH2LP02K**	**UVH2LT02K**
24 Vac	**U09**	**U10**	**U11**	**U12**	**UVH2LP03K**	**UVH2LT03K**
48–60 Vac	**U13**	**U14**	**U15**	**U16**	**UVH2LP05K**	**UVH2LT05K**
110–127 Vac	**U17**	**U18**	**U19**	**U20**	**UVH2LP08K**	**UVH2LT08K**
208–240 Vac	**U21**	**U22**	**U23**	**U24**	**UVH2LP11K**	**UVH2LT11K**
380–480 Vac	**U25**	**U26**	**U27**	**U28**	**UVH2LP15K**	**UVH2LT15K**
Right-Pole Mounting AC Ratings ③						
12 Vac	**U37**	**U38**	**U39**	**U40**	**UVH2RP02K**	**UVH2RT02K**
24 Vac	**U41**	**U42**	**U43**	**U44**	**UVH2RP03K**	**UVH2RT03K**
48–60 Vac	**U45**	**U46**	**U47**	**U48**	**UVH2RP05K**	**UVH2RT05K**
110–127 Vac	**U49**	**U50**	**U51**	**U52**	**UVH2RP08K**	**UVH2RT08K**
208–240 Vac	**U53**	**U54**	**U55**	**U56**	**UVH2RP11K**	**UVH2RT11K**
380–480 Vac	**U57**	**U58**	**U59**	**U60**	**UVH2RP15K**	**UVH2RT15K**
Left-Pole Mounting DC Ratings ④						
12 Vdc	**T01**	**T02**	**T03**	**T04**	**UVH2LP20K**	**UVH2LT20K**
24 Vdc	**T05**	**T06**	**T07**	**T08**	**UVH2LP21K**	**UVH2LT21K**
48–60 Vdc	**T09**	**T10**	**T11**	**T12**	**UVH2LP23K**	**UVH2LT23K**
110–127 Vdc	**T13**	**T14**	**T15**	**T16**	**UVH2LP26K**	**UVH2LT26K**
220–250 Vdc	**T17**	**T18**	**T19**	**T20**	**UVH2LP28K**	**UVH2LT28K**
Right-Pole Mounting DC Ratings ③						
12 Vdc	**T21**	**T22**	**T23**	**T24**	**UVH2RP20K**	**UVH2RT20K**
24 Vdc	**T25**	**T26**	**T27**	**T28**	**UVH2RP21K**	**UVH2RT21K**
48–60 Vdc	**T29**	**T30**	**T31**	**T32**	**UVH2RP23K**	**UVH2RT23K**
110–127 Vdc	**T33**	**T34**	**T35**	**T36**	**UVH2RP26K**	**UVH2RT26K**
220–250 Vdc	**T37**	**T38**	**T39**	**T40**	**UVH2RP28K**	**UVH2RT28K**

Notes

① For electrical rating data for manual, automatic and electrical reset undervoltage release mechanisms, refer to Eaton.
② Listed with Underwriters Laboratories for field installation under E64983.
③ Not for use on right pole of four-pole circuit breakers.
④ Standard mounting location—leads exit rear of breaker.

K-Frame and HMCP (K) Undervoltage Release Mechanism

	Factory Mounted Connection Type and Location				Field Mounted Field Installation Kits ①	
	18-Inch (457.2 mm) Pigtail Leads			Terminal Block		
	Same Side	Rear ②	Opposite Side	Same Side	Pigtail Leads	Terminal Block
Voltage Rating (AC Freq. = 50/60 Hz)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
Left-Pole Mounting AC Ratings ②						
12 Vac	**U05**	**U06**	**U07**	**U08**	**UVH3LP02K**	**UVH3LT02K**
24 Vac	**U09**	**U10**	**U11**	**U12**	**UVH3LP03K**	**UVH3LT03K**
48–60 Vac	**U13**	**U14**	**U15**	**U16**	**UVH3LP05K**	**UVH3LT05K**
110–127 Vac	**U17**	**U18**	**U19**	**U20**	**UVH3LP08K**	**UVH3LT08K**
208–240 Vac	**U21**	**U22**	**U23**	**U24**	**UVH3LP11K**	**UVH3LT11K**
380–480 Vac	**U25**	**U26**	**U27**	**U28**	**UVH3LP15K**	**UVH3LT15K**
Right-Pole Mounting AC Ratings ③④⑤						
12 Vac	**U37**	**U38**	**U39**	**U40**	**UVH3RP02K**	**UVH3RT02K**
24 Vac	**U41**	**U42**	**U43**	**U44**	**UVH3RP03K**	**UVH3RT03K**
48–60 Vac	**U45**	**U46**	**U47**	**U48**	**UVH3RP05K**	**UVH3RT05K**
110–127 Vac	**U49**	**U50**	**U51**	**U52**	**UVH3RP08K**	**UVH3RT08K**
208–240 Vac	**U53**	**U54**	**U55**	**U56**	**UVH3RP11K**	**UVH3RT11K**
380–480 Vac	**U57**	**U58**	**U59**	**U60**	**UVH3RP15K**	**UVH3RT15K**
Left-Pole Mounting DC Ratings ②						
12 Vdc	**T01**	**T02**	**T03**	**T04**	**UVH3LP20K**	**UVH3LT20K**
24 Vdc	**T05**	**T06**	**T07**	**T08**	**UVH3LP21K**	**UVH3LT21K**
48–60 Vdc	**T09**	**T10**	**T11**	**T12**	**UVH3LP23K**	**UVH3LT23K**
110–127 Vdc	**T13**	**T14**	**T15**	**T16**	**UVH3LP26K**	**UVH3LT26K**
220–250 Vdc	**T17**	**T18**	**T19**	**T20**	**UVH3LP28K**	**UVH3LT28K**
Right-Pole Mounting DC Ratings ③④⑤						
12 Vdc	**T21**	**T22**	**T23**	**T24**	**UVH3RP20K**	**UVH3RT20K**
24 Vdc	**T25**	**T26**	**T27**	**T28**	**UVH3RP21K**	**UVH3RT21K**
48–60 Vdc	**T29**	**T30**	**T31**	**T32**	**UVH3RP23K**	**UVH3RT23K**
110–127 Vdc	**T33**	**T34**	**T35**	**T36**	**UVH3RP26K**	**UVH3RT26K**
220–250 Vdc	**T37**	**T38**	**T39**	**T40**	**UVH3RP28K**	**UVH3RT28K**

Notes

① Listed with Underwriters Laboratories, for field installation under E64983.

② Standard mounting location—leads exit rear of breaker.

③ For use with KT (thermal-magnetic) trip units only.

④ Not for use on right pole of four-pole circuit breaker.

⑤ Breakers with K-Frame OPTIM 550 can only accept accessories in left pole.

L-, HMCP (L) and (M)-Frames and Undervoltage Release Mechanism

	Factory Mounted Connection Type and Location				Field Mounted Field Installation Kits ①	
	18-Inch (457.2 mm) Pigtail Leads			Terminal Block		
	Same Side	Rear ②	Opposite Side	Same Side	Pigtail Leads	Terminal Block
Voltage Rating (AC Freq. = 50/60 Hz)	Suffix Number	Suffix Number	Suffix Number	Suffix Number	Catalog Number	Catalog Number
Left-Pole Mounting AC Ratings ②						
12 Vac	U05	U06	U07	U08	UVH4LP02K	UVH4LT02K
24 Vac	U09	U10	U11	U12	UVH4LP03K	UVH4LT03K
48–60 Vac	U13	U14	U15	U16	UVH4LP05K	UVH4LT05K
110–127 Vac	U17	U18	U19	U20	UVH4LP08K	UVH4LT08K
208–240 Vac	U21	U22	U23	U24	UVH4LP11K	UVH4LT11K
380–480 Vac	U25	U26	U27	U28	UVH4LP15K	UVH4LT15K
Right-Pole Mounting AC Ratings ③④						
12 Vac	U37	U38	U39	U40	UVH4RP02K	UVH4RT02K
24 Vac	U41	U42	U43	U44	UVH4RP03K	UVH4RT03K
48–60 Vac	U45	U46	U47	U48	UVH4RP05K	UVH4RT05K
110–127 Vac	U49	U50	U51	U52	UVH4RP08K	UVH4RT08K
208–240 Vac	U53	U54	U55	U56	UVH4RP11K	UVH4RT11K
380–480 Vac	U57	U58	U59	U60	UVH4RP15K	UVH4RT15K
Left-Pole Mounting DC Ratings ②						
12 Vdc	T01	T02	T03	T04	UVH4LP20K	UVH4LT20K
24 Vdc	T05	T06	T07	T08	UVH4LP21K	UVH4LT21K
48–60 Vdc	T09	T10	T11	T12	UVH4LP23K	UVH4LT23K
110–127 Vdc	T13	T14	T15	T16	UVH4LP26K	UVH4LT26K
220–250 Vdc	T17	T18	T19	T20	UVH4LP28K	UVH4LT28K
Right-Pole Mounting DC Ratings ③④						
12 Vdc	T21	T22	T23	T24	UVH4RP20K	UVH4RT20K
24 Vdc	T25	T26	T27	T28	UVH4RP21K	UVH4RT21K
48–60 Vdc	T29	T30	T31	T32	UVH4RP23K	UVH4RT23K
110–127 Vdc	T33	T34	T35	T36	UVH4RP26K	UVH4RT26K
220–250 Vdc	T37	T38	T39	T40	UVH4RP28K	UVH4RT28K

Notes

① Listed with Underwriters Laboratories for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ For use with LT (thermal-magnetic) trip units only.
④ Not for use on right pole of four-pole circuit breaker.

N-Frame and HMCP (N) Undervoltage Release Mechanism

Voltage Rating (AC Freq. = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Same Side Suffix Number	Rear ② Suffix Number	Opposite Side Suffix Number	Terminal Block Same Side Suffix Number	Field Mounted Field Installation Kits ① Pigtail Leads Catalog Number	Terminal Block Catalog Number
Left-Pole Mounting AC Ratings ②						
12 Vac	**U05**	**U06**	**U07**	**U08**	**UVH5LP02K**	**UVH5LT02K**
24 Vac	**U09**	**U10**	**U11**	**U12**	**UVH5LP03K**	**UVH5LT03K**
48–60 Vac	**U13**	**U14**	**U15**	**U16**	**UVH5LP05K**	**UVH5LT05K**
110–127 Vac	**U17**	**U18**	**U19**	**U20**	**UVH5LP08K**	**UVH5LT08K**
208–240 Vac	**U21**	**U22**	**U23**	**U24**	**UVH5LP11K**	**UVH5LT11K**
380–480 Vac	**U25**	**U26**	**U27**	**U28**	**UVH5LP29K**	**UVH5LT29K**
Left-Pole Mounting DC Ratings ②						
12 Vdc	**T01**	**T02**	**T03**	**T04**	**UVH5LP20K**	**UVH5LT20K**
24 Vdc	**T05**	**T06**	**T07**	**T08**	**UVH5LP21K**	**UVH5LT21K**
48–60 Vdc	**T09**	**T10**	**T11**	**T12**	**UVH5LP23K**	**UVH5LT23K**
110–127 Vdc	**T13**	**T14**	**T15**	**T16**	**UVH5LP26K**	**UVH5LT26K**
220–250 Vdc	**T17**	**T18**	**T19**	**T20**	**UVH5LP28K**	**UVH5LT28K**

R-Frame Undervoltage Release Mechanism (RH only)

Voltage Rating (AC Frequency = 50/60 Hz)	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads Suffix Number ④	Field Mounted Field Installation Kits ③ Pigtail Leads Catalog Number ④
12 Vac	**U37**	**UVH6RP02K**
24 Vac	**U41**	**UVH6RP03K**
48–60 Vac	**U45**	**UVH6RP05K**
110–127 Vac	**U49**	**UVH6RP08K**
208–240 Vac	**U53**	**UVH6RP11K**
380–500 Vac	**U57**	**UVH6RP29K**
12 Vdc	**T21**	**UVH6RP20K**
24 Vdc	**T25**	**UVH6RP21K**
48–60 Vdc	**T29**	**UVH6RP23K**
110–125 Vdc	**T33**	**UVH6RP26K**
220–250 Vdc	**T37**	**UVH6RP28K**

Notes

① Listed with Underwriters Laboratories for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ Endurance: 500 electrical operations plus 2500 mechanical operations.
④ Pigtail wire size: 18 AWG (0.82 mm^2). Leads are orange and brown.

Accessory Terminal Block (R-Frame)

Accessory Terminal Block (R-Frame)

R-Frame Accessory Terminal Block ①

Factory Installed Suffix Number	Field Mounted Catalog Number
Q01	**TBRDK**

Number of Control Wires for Each Internally Mounted Accessory

Type of Accessory	Number of Contacts per Single Accessory	Required Number of Wires
Auxiliary switch	2a/2b 4a/4b	6 12
Alarm (Signal)/ Lockout switch	1m/1b 2m/2b	6 12
Shunt trip	N/A	2
Low energy shunt	N/A	2
Undervoltage release mechanism	N/A	2

PowerNet and Zone Interlock Kits (OPTIM 550 Only)
K-, L- and N-Frames

PowerNet and Zone Interlock Kits

PowerNet Interlock Kit ②

Circuit Breaker	Factory Install Suffix	Catalog Number
K-Frame	**PN**	**ICK550K**
L-Frame	**PN**	**ICK550L**
N-Frame	**PN**	**ICK550N**

Zone Interlock/Ground Kit ②③

Circuit Breaker	Factory Install Suffix	Catalog Number
K-Frame	**ZG**	**ZGK550K**
L-Frame	**ZG**	**ZGK550L**
N-Frame	**ZG**	**ZGK550N**

PowerNet and Zone Interlock/Ground Kit ②③

Circuit Breaker	Factory Install Suffix	Catalog Number
K-Frame	**ZGP**	**ZGPK550K**
L-Frame	**ZGP**	**ZGPK550L**
N-Frame	**ZGP**	**ZGPK550N**

Notes

① One 24-point accessory terminal block provided with circuit breaker when ordered factory installed or shipped from warehouse as separate item when ordered for field installation. See Digitrip RMS master connection diagram (IL 29C714).

② Installation of these kits restrict any other attachments from being installed in the RH pole.

③ Includes a ground fault alarm signal that can drive the ground fault alarm unit (catalog number GFAU).

Technical Data and Specifications

Alarm Switch

F-Frame Electrical Rating Data ①②

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
Multi-Pole Circuit Breakers			
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500
Single-Pole Circuit Breakers			
125/250	50/60 Hz	6 ③	2000
28	DC	3 ③	2000
28	DC	5 ④	2000

J-Frame Electrical Rating Data ⑤⑥

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

K-Frame Electrical Rating Data ⑥⑦

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

L- and M-Frames Electrical Rating Data ⑥⑦

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

N-Frame Electrical Rating Data ⑧

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

R-Frame Electrical Rating Data ⑨⑩

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

Auxiliary Switch

F-Frame Electrical Rating Data ①②

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
125 ③	50/60 Hz	1	2500
600	50/60 Hz	6	2500
125	DC	0.50 ④	2500
250	DC	0.25 ④	2500

J-Frame Electrical Rating Data ①②

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ④	2500
250	DC	0.25 ④	2500

K-Frame Electrical Rating Data ②⑤

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ④	2500
250	DC	0.25 ④	2500

L- and M-Frames Electrical Rating Data ②

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ④	2500
250	DC	0.25 ④	2500

N-Frame Electrical Rating Data ②⑥

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ④	2500
250	DC	0.25 ④	2500

R-Frame Electrical Rating Data ⑦⑧

Maximum Voltage	Frequency	Maximum Current Amperes
600	50/60 Hz	6
125	DC	0.50 ④
250	DC	0.25 ④

Notes

① Endurance: 6000 electrical operations plus 4000 mechanical operations.
② Endurance: 6000 electrical operations plus 2000 mechanical operations.
③ Non-inductive load.
④ Inductive (L/R = 0.026).
⑤ Endurance: 6000 electrical operations plus 2000 mechanical operations.
⑥ Pigtail wire size: 18 AWG (0.82 mm^2).
⑦ Endurance: 5000 electrical operations plus 1000 mechanical operations.
⑧ Endurance: 3000 electrical operations plus 1000 mechanical operations.
⑨ Endurance: 500 electrical operations plus 2500 mechanical operations.
⑩ Pigtail wire size: 18 AWG (0.82 mm^2). Leads are red, black and blue.

Auxiliary Switch and Alarm Switch Combination

F-Frame Electrical Rating Data ①②

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2200
250	DC	0.25 ③	2200

J-Frame Electrical Rating Data ②⑤

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

K-Frame Electrical Rating Data ②⑦

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

L- and M-Frames Electrical Rating Data ②⑦

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

N-Frame Electrical Rating Data ②⑧

Maximum Voltage	Frequency	Maximum Current Amperes	Dielectric Withstand Voltage
600	50/60 Hz	6	2500
125	DC	0.50 ③	2500
250	DC	0.25 ③	2500

Notes

① Endurance: 6000 electrical operations plus 4000 mechanical operations.
② Pigtail wire size: 18 AWG (0.82 mm^2).
③ Non-inductive load.
④ Endurance: 6000 electrical operations plus 2000 mechanical operations.
⑤ Endurance: 5000 electrical operations plus 1000 mechanical operations.
⑥ Endurance: 3000 electrical operations plus 1000 mechanical operations.

2

Shunt Trip

F-Frame and HMCP Shunt Trip Electrical Rating Data ①②③

	Application Ratings		Electrical Operating Ratings						
Catalog Number	Voltage (V)	Frequency (Hz)	Supply Voltage (V)	Minimum Operating Voltage (V)	I_p (A)	I_{rms} at 0.25 (A)	I_{rms} at 0.33s (A)	VA	One Minute Dielectric Withstand Voltage (V)
SNT1LP03K or SNT1LT03K	12–24	50/60	9	6.3	6.1		4.3	40	1048
			12		8.5		6	75	
			24		17		12	300	
	12–24	DC	12	9		8		100	
			24			16		400	
SNT1LP08K or SNT1LT08K	48–127	50/60	48	33.6	2.7		1.9	92	1254
			60		3.4		2.4	140	
			110		6.2		4.4	480	
			120		6.8		4.8	570	
			127		7.2		5.1	640	
	48–60	DC	48	33.6		2.1		100	
			60			2.6		160	
SNT1LP12K or SNT1LT12K	208–380	50/60	208	146	1.2		0.25	180	1760
			220		1.3		0.27	200	
			240		1.4		0.29	240	
			380		2.3		0.31	610	
	110–125	DC	110	77		0.5		55	
			120			0.55		66	
			125			0.57		71	
SNT1LP18K or SNT1LT18K	415–600	50/60	400	280	1.1		0.77	310	2200
			415		1.1		0.8	330	
			440		1.2		0.85	380	
			480		1.3		0.93	450	
			525		1.4		1.02	530	
			550		1.5		1.06	590	
			600		1.6		1.16	700	
	220–250	DC	220	154		0.48		110	
			250			0.55		140	

Notes

① Average unlatching time: 6 milliseconds.

② Average circuit breaker contact total opening time: 18 milliseconds.

③ Endurance: 6000 electrical operations plus 4000 mechanical operations.

J-Frame and HMCP (J) Shunt Trip Electrical Rating Data ①②③

	Application Ratings		Electrical Operating Ratings						
Catalog Number	Voltage (V)	Frequency (Hz)	Supply Voltage (V)	Minimum Operating Voltage (V)	I_p (A)	I_{rms} at 0.25 (A)	I_{rms} at 0.33s (A)	VA	One Minute Dielectric Withstand Voltage (V)
SNT2P04K or SNT2T04K	12–24	50/60	12	9	17.7		12.6	164	1048
			24		38.3		27.4	631	
	12–24	DC	12	9		7.3		87	
			24			16.9		405	
SNT2P06K or SNT2T06K	48–60	50/60	48	36	24.4		17.3	830	1120
			60		30.1		21.3	1280	
	48–60	DC	48	36		14.8		710	
			60			18.4		1105	
SNT2P11K or SNT2T11K	110–240	50/60	110	60	0.9		0.6	66	1480
			120		1		0.7	84	
			127		1.1		0.8	102	
			208		2.4		1.7	354	
			220		2.6		1.8	396	
			240		2.6		1.8	432	
	110–125	DC	110	60		1		112	
			120			1.1		138	
			125			1.2		150	
SNT2P14K or SNT2T14K	380–440	50/60	380	285	0.34		0.25	127	1880
			400		0.38		0.27	150	
			415		0.4		0.29	163	
			440		0.44		0.31	188	
	220–250	DC	220	165		0.19		40	
			250			0.22		58	
SNT2P18K or SNT2T18K	480–600	50/60	480	360	0.13		0.07	34	2200
			525		0.13		0.08	42	
			550		0.13		0.09	50	
			600		0.14		0.1	60	

Notes

① Average unlatching time: 6 milliseconds.
② Average circuit breaker contact total opening time: 18 milliseconds.
③ Endurance: 6000 electrical operations plus 2000 mechanical operations.

K-Frame and HMCP (K) Shunt Trip Electrical Rating Data ③②③

	Application Ratings			Electrical Operating Ratings					
Catalog Number	Voltage (V)	Frequency (Hz)	Supply Voltage (V)	Minimum Operating Voltage (V)	I_p (A)	I_{rms} at 0.25 (A)	I_{rms} at 0.33s (A)	VA	One Minute Dielectric Withstand Voltage (V)
SNT3P04K or SNT3T04K	12–24	50/60	12	9	17.7		12.6	164	1048
			24		38.3		27.4	631	
	12–24	DC	12	9		7.3		87	
			24			16.9		405	
SNT3P06K or SNT3T06K	48–60	50/60	48	36	24.4		17.3	830	1120
			60		30.1		21.3	1280	
	48–60	DC	48	36		14.8		710	
			60			18.4		1105	
SNT3P11K or SNT3T11K	110–240	50/60	110	60	1.3		0.9	100	1480
			120		1.4		1	120	
			127		1.5		1.1	140	
			208		2.8		2	420	
			220		3		2.1	470	
			240		3.2		2.3	550	
	110–125	DC	110	82		1		110	
			120			1.1		130	
			125			1.2		140	
SNT3P14K or SNT3T14K	380–440	50/60	380	285	0.37		0.25	95	1880
			400		0.39		0.27	108	
			415		0.42		0.29	120	
			440		0.44		0.31	136	
	220–250	DC	220	165		0.19		41	
			250			0.22		54	
SNT3P18K or SNT3T18K	480–600	50/60	480	360	0.11		0.08	40	2200
			525		0.13		0.09	50	
			550		0.13		0.09	50	
			600		0.16		0.12	70	

Notes

① Approximate unlatching time: 6 milliseconds.

② Approximate total circuit breaker contact opening time: 8 milliseconds.

③ Endurance: 5000 electrical operations plus 1000 mechanical operations.

L-Frame and HMCP (L) and M-Frame Shunt Trip Electrical Rating Data ①②③

	Application Ratings		Electrical Operating Ratings						
Catalog Number	Voltage (V)	Frequency (Hz)	Supply Voltage (V)	Minimum Operating Voltage (V)	I_p (A)	I_{rms} at 0.25 (A)	I_{rms} at 0.33s (A)	VA	One Minute Dielectric Withstand Voltage (V)
SNT4P03K or SNT4T03K	12–24	50/60	9	6.3	7.2		5.1	46	1048
			12		11.6		8.2	98	
			24		28.6		20.2	485	
	12–24	DC	9	6.3		8.5		75	
			12			8.6		103	
			24			17.4		418	
SNT4P05K SNT4T05K	48–60	50/60	48	34	0.72		0.51	82	1120
			60		1.2		0.84	126	
SNT4P11K or SNT4T11K	110–240	50/60	110	77	0.89		0.63	69	1480
			120		1.03		0.73	88	
			127		1.1		0.8	102	
			208		2.3		1.6	333	
			220		2.4		1.7	374	
			240		2.6		1.8	432	
SNT4P14K or SNT4T14K	380–440	50/60	380	266	0.3		0.21	80	1880
			400		0.34		0.24	96	
			415		0.35		0.25	104	
			440		0.38		0.27	119	
	220–250	DC	220	154		0.34		75	
			250			0.34		85	
SNT4P18K or SNT4T18K	480–600	50/60	480	336	0.07		0.05	24	2200
			525		0.08		0.06	32	
			550		0.09		0.07	39	
			600		0.11		0.08	48	
SNT4P23K SNT4T23K	48–60	DC	48	34		0.76		36	1120
			60			0.95		57	
SNT4P26K or SNT4T26K	110–125	DC	110	77		0.42		46	1250
			120			0.43		52	
			125			0.44		55	

Notes

① Approximate unlatching time: 6 milliseconds.
② Approximate total circuit breaker contact opening time: 18 milliseconds.
③ Endurance: 5000 electrical operations plus 1000 mechanical operations.

N-Frame and HMCP (N) Shunt Trip Electrical Rating Data ①②③

	Application Ratings			Electrical Operating Ratings					
Catalog Number	**Voltage (V)**	**Frequency (Hz)**	**Supply Voltage (V)**	**Minimum Operating Voltage (V)**	**I_p (A)**	**I_{rms} at 0.25 (A)**	**I_{rms} at 0.33s (A)**	**VA**	**One Minute Dielectric Withstand Voltage (V)**
SNT5LP03K or SNT5LT03K	9–24	50/60	9	6.3	7.2		5.1	46	1048
			12		11.6		8.2	98	
			24		28		19.8	475	
	9–24	DC	9	7.2		8.8		79	
			12			12.1		145	
			24			25.4		610	
SNT5LP05K SNT5LT05K	48–60	50/60	48	34	2.4		1.7	82	1120
			60		3		2.1	126	
SNT5LP11K or SNT5LT11K	110–240	50/60	110	77	0.86		0.61	67	1480
			120		0.98		0.69	83	
			127		1.1		0.75	95	
			208		2.3		1.6	333	
			220		2.4		1.7	374	
			240		2.6		1.8	432	
SNT5LP14K or SNT5LT14K	380–440	50/60	380	266	0.28		0.2	76	1880
			400		0.31		0.22	88	
			415		0.33		0.23	95	
			440		0.35		0.25	110	
	220–250	DC	220	154		0.21		46	
			250			0.22		55	
SNT5LP18K or SNT5LT18K	480–600	50/60	480	336	0.06		0.04	19	2200
			525		0.08		0.06	32	
			550		0.08		0.06	33	
			600		0.1		0.07	42	
SNT5LP23K SNT5LT23K	48–60	DC	48	34		1.4		67	1120
			60			1.7		102	
SNT5LP26K or SNT5LT26K	110–125	DC	110	77		1.1		121	1250
			120			1.2		144	
			125			1.2		150	

Notes

① Approximate unlatching time: 6 milliseconds.
② Approximate total circuit breaker contact opening time: 18 milliseconds.
③ Endurance: 3000 electrical operations plus 1000 mechanical operations.

R-Frame Shunt Trip Electrical Rating Data ①②③④⑤⑥

	Application Ratings		Electrical Operating Ratings						
Catalog Number	Voltage (V)	Frequency (Hz)	Supply Voltage (V)	Minimum Operating Voltage (V)	I_p (A)	I_{rms} at 0.25 (A)	I_{rms} at 0.33s (A)	VA	One Minute Dielectric Withstand Voltage (V)
SNT6P03K	24	50/60	24	16.8	36.1		25.5	612	1050
	24	DC	24	16.8		16.5		396	
SNT6P05K	48–60	50/60	48	34	11.9		8.4	403	1120
			60		15.7		11.1	666	
SNT6P11K	110–240	50/60	110	60	5.09		3.6	396	1480
			120		5.66		4	480	
			127		5.94		4.2	533	
			208		10.2		7.2	1498	
			220		10.5		7.4	1628	
			240		11.2		7.9	1896	
SNT6P14K	380–440	50/60	380	266	5.94		4.2	1596	2200
			400		6.23		4.4	1760	
			415		6.51		4.6	1909	
			440		6.93		4.9	2156	
	220–250	DC	220	154		1.7		374	1500
			250			1.9		475	
SNT6P18K	480–600	50/60	480	336	0.68		0.48	230	2200
			525		0.78		0.55	289	
			550		0.79		0.56	308	
			600		0.91		0.64	384	
SNT6P23K	48–60	DC	48	34		7.1		341	1120
			60			8.8		258	
SNT6P26K	110–125	DC	110	77		2.4		264	1250
			120			2.6		312	
			125			2.8		350	

Notes

① Approximate unlatching time of 6 milliseconds.
② Average circuit breaker contact total opening time approximately 62 milliseconds, at rated voltage.
③ Endurance: 500 electrical operations and 2500 mechanical operations.
④ Shunt trip can be operated up to a maximum of six times per minute.
⑤ Maximum operating voltage—110% of maximum voltage range rating.
⑥ Pigtail wire size: 18 AWG (0.82 mm^2). Leads are yellow and white.

Undervoltage Release Mechanism

F-Frame Electrical Rating Data ①

50/60 Hz					DC				
	Dropout Voltage		Pickup Voltage			Dropout Voltage		Pickup Voltage	
Supply Voltage	Minimum	Maximum	Maximum	VA	Supply Voltage	Minimum	Maximum	Maximum	VA
12	4.2	6.3	7.6	1.3	12	4.2	8.4	10.2	2.8
12	4.2	6.3	7.6	2.5	12	4.2	8.4	10.2	2.8
24	8.4	16.8	20.4	1.4	24	8.4	16.8	20.4	1.6
48	21.0	33.6	40.8	1.2	48	21.0	33.6	40.8	1.3
60	21.0	33.6	40.8	1.9	60	21.0	33.6	40.8	2.0
110	44.5	77.0	93.5	1.3	110	44.5	77.0	93.5	1.5
120	44.5	77.0	93.5	1.5	120	44.5	77.0	93.5	1.7
127	44.5	77.0	93.5	1.7	125	44.5	77.0	93.5	1.9
208	84.0	145.6	176.8	2.2	220	87.5	154.0	187.0	2.6
220	84.0	145.6	176.8	2.4	250	87.5	154.0	187.0	3.4
240	84.0	145.6	176.8	2.9	—	—	—	—	—
380	168.0	266.0	323.0	2.9	—	—	—	—	—
415	168.0	266.0	323.0	3.5	—	—	—	—	—
440	168.0	266.0	323.0	3.9	—	—	—	—	—
480	168.0	266.0	323.0	4.6	—	—	—	—	—
525	210.0	367.0	446.0	4.3	—	—	—	—	—
550	210.0	367.0	446.0	4.8	—	—	—	—	—
600	210.0	367.0	446.0	5.8	—	—	—	—	—

J-Frame Electrical Rating Data ②③

50/60 Hz					DC				
	Dropout Voltage		Pickup Voltage			Dropout Voltage		Pickup Voltage	
Supply Voltage	Minimum	Maximum	Maximum	VA	Supply Voltage	Minimum	Maximum	Maximum	VA
12	4.2	8.4	10.2	1.9	12	4.2	8.4	10.2	1.6
24	8.4	16.8	20.4	3.9	24	8.4	16.8	20.4	3.1
48	21.0	33.6	40.8	2.5	48	21.0	33.6	40.8	2.0
60	21.0	33.6	40.8	3.8	60	21.0	33.6	40.8	3.1
110	44.5	77.0	93.5	1.8	110	44.5	77.0	93.5	1.6
120	44.5	77.0	93.5	2.1	120	44.5	77.0	93.5	1.9
127	44.5	77.0	93.5	2.4	125	44.5	77.0	93.5	2.2
208	84.0	145.6	176.8	2.7	220	87.5	154.0	187.0	3.1
220	84.0	145.6	176.8	3.1	250	87.5	154.0	187.0	4.0
240	84.0	145.6	176.8	3.8	—	—	—	—	—
380	168.0	266.0	323.0	3.4	—	—	—	—	—
415	168.0	266.0	323.0	4.0	—	—	—	—	—
440	168.0	266.0	323.0	4.6	—	—	—	—	—
480	168.0	266.0	323.0	5.4	—	—	—	—	—

Notes

① Endurance: 6000 electrical operations plus 4000 mechanical operations.
② Endurance: 6000 electrical operations plus 2000 mechanical operations.
③ For electrical rating data for manual, automatic and electrical reset undervoltage release mechanisms, refer to Eaton.

K-Frame Electrical Rating Data ①

50/60 Hz					DC				
	Dropout Voltage		Pickup Voltage			Dropout Voltage		Pickup Voltage	
Supply Voltage	Minimum	Maximum	Maximum	VA	Supply Voltage	Minimum	Maximum	Maximum	VA
12	4.2	8.4	10.2	1.9	12	4.2	8.4	10.2	1.6
24	8.4	16.8	20.4	3.9	24	8.4	16.8	20.4	3.1
48	21.0	33.6	40.8	2.5	48	21.0	33.6	40.8	2.0
60	21.0	33.6	40.8	3.8	60	21.0	33.6	40.8	3.1
110	44.5	77.0	93.5	1.8	110	44.5	77.0	93.5	1.6
120	44.5	77.0	93.5	2.1	120	44.5	77.0	93.5	1.9
127	44.5	77.0	93.5	2.4	125	44.5	77.0	93.5	2.2
208	84.0	145.6	176.8	2.7	220	87.5	154.0	187.0	3.1
220	84.0	145.6	176.8	3.1	250	87.5	154.0	187.0	4.0
240	84.0	145.6	176.8	3.8	—	—	—	—	—
380	168.0	266.0	323.0	3.4	—	—	—	—	—
415	168.0	266.0	323.0	4.0	—	—	—	—	—
440	168.0	266.0	323.0	4.6	—	—	—	—	—
480	168.0	266.0	323.0	5.4	—	—	—	—	—

L- and M-Frames Electrical Rating Data ①

50/60 Hz					DC				
	Dropout Voltage		Pickup Voltage			Dropout Voltage		Pickup Voltage	
Supply Voltage	Minimum	Maximum	Maximum	VA	Supply Voltage	Minimum	Maximum	Maximum	VA
12	4.2	8.4	10.2	1.9	12	4.2	8.4	10.2	1.6
24	8.4	16.8	20.4	3.9	24	8.4	16.8	20.4	3.1
48	21.0	33.6	40.8	2.5	48	21.0	33.6	40.8	2.0
60	21.0	33.6	40.8	3.8	60	21.0	33.6	40.8	3.1
110	44.5	77.0	93.5	1.8	110	44.5	77.0	93.5	1.6
120	44.5	77.0	93.5	2.1	120	44.5	77.0	93.5	1.9
127	44.5	77.0	93.5	2.4	125	44.5	77.0	93.5	2.2
208	84.0	145.6	176.8	2.7	220	87.5	154.0	187.0	3.1
220	84.0	145.6	176.8	3.1	250	87.5	154.0	187.0	4.0
240	84.0	145.6	176.8	3.8	—	—	—	—	—
380	168.0	266.0	323.0	3.4	—	—	—	—	—
415	168.0	266.0	323.0	4.0	—	—	—	—	—
440	168.0	266.0	323.0	4.6	—	—	—	—	—
480	168.0	266.0	323.0	5.4	—	—	—	—	—

Note

① Endurance: 5000 electrical operations plus 1000 mechanical operations.

N-Frame Electrical Rating Data ①

50/60 Hz					DC				
	Dropout Voltage		Pickup Voltage			Dropout Voltage		Pickup Voltage	
Supply Voltage	Minimum	Maximum	Maximum	VA	Supply Voltage	Minimum	Maximum	Maximum	VA
12	4.2	8.4	10.2	1.9	12	4.2	8.4	10.2	1.6
24	8.4	16.8	20.4	3.9	24	8.4	16.8	20.4	3.1
48	21.0	33.6	40.8	2.5	48	21.0	33.6	40.8	2.0
60	21.0	33.6	40.8	3.8	60	21.0	33.6	40.8	3.1
110	44.5	77.0	93.5	1.8	110	44.5	77.0	93.5	1.6
120	44.5	77.0	93.5	2.1	120	44.5	77.0	93.5	1.9
127	44.5	77.0	93.5	2.4	125	44.5	77.0	93.5	2.2
208	84.0	145.6	176.8	2.7	220	87.5	154.0	187.0	3.1
220	84.0	145.6	176.8	3.1	220	87.5	154.0	187.0	—
240	84.0	145.6	176.8	3.8	250	—	—	—	4.0
380	175.0	266.0	323.0	3.4	—	—	—	—	—
415	175.0	266.0	323.0	4.0	—	—	—	—	—
480	175.0	266.0	323.0	4.6	—	—	—	—	—
500	175.0	266.0	323.0	5.4	—	—	—	—	—

Note

① Endurance: 3000 electrical operations plus 1000 mechanical operations.

R-Frame AC Undervoltage Release Mechanism (Handle Reset) Ratings ①②

Catalog Suffix	Application Ratings Voltage (V)	Electrical Operating Ratings Supply Voltage (V)	Dropout Voltage (V) Minimum	Dropout Voltage (V) Maximum	Pickup Voltage (V) Max.	Approximate Operating Time (ms) VA	Minimum UVR Response ③	Initiation Circuit Breaker Contact Separation ④	Maximum Circuit Breaker Contact Opening	Dielectric Withstand Voltage (V) ⑤
02/02K	12	12	4.2	8.4	10.2	2.3	5	46	77	1024
03/03K	24	24	8.4	16.8	20.4	3.1	5	46	77	1048
05/05K	48–60	48	21.0	33.5	40.8	3.4	5	46	77	1120
		60	21.0	33.5	40.8	6.0	5	46	77	1120
08/08K	110–127	110	44.5	77.0	93.5	3.3	5	46	77	1254
		120	44.5	77.0	93.5	3.6	5	46	77	1254
		127	44.5	77.0	93.5	3.8	5	46	77	1254
11/11K	208–240	208	84.0	145.6	176.8	4.2	5	46	77	1480
		220	84.0	145.6	176.8	6.6	5	46	77	1480
		240	84.0	145.6	176.8	7.2	5	46	77	1480
29/29K	380–500	380	168.0	266.0	323.0	3.8	5	46	77	2000
		415	168.0	266.0	323.0	8.3	5	46	77	2000
		440	168.0	266.0	323.0	8.8	5	46	77	2000
		480	168.0	266.0	323.0	9.6	5	46	77	2000
		500	168.0	266.0	323.0	10.0	5	46	77	2000

R-Frame DC Undervoltage Release Mechanism (Handle Reset) Ratings ①②

Catalog Suffix	Application Ratings Voltage (V)	Electrical Operating Ratings Supply Voltage (V)	Dropout Voltage (V) Minimum	Dropout Voltage (V) Maximum	Pickup Voltage (V) Max.	Approximate Operating Time (ms) VA	Minimum UVR Response ③	Initiation Circuit Breaker Contact Separation ④	Maximum Circuit Breaker Contact Opening	Dielectric Withstand Voltage (V) ⑤
20/20K	12	12	4.2	8.4	10.2	3.4	5	46	77	1024
21/21K	24	24	8.4	16.8	20.4	4.3	5	46	77	1048
23/23K	48–60	48	21.0	33.5	40.8	4.8	5	46	77	1120
		60	21.0	33.5	40.8	7.2	5	46	77	1120
26/26K	110–127	110	43.8	77.0	93.5	3.3	5	46	77	1250
		120	43.8	77.0	93.5	3.6	5	46	77	1250
		125	43.8	77.0	93.5	3.8	5	46	77	1250
28/28K	220–250	220	87.5	154.0	187.0	6.6	5	46	77	1500
		250	87.5	154.0	187.0	7.5	5	46	77	1500

Notes

① Endurance: 500 electrical operations plus 2500 mechanical operations.
② Pigtail wire size: 18 AWG (0.82 mm^2). Leads are orange and brown.
③ UVR will override a momentary voltage dip up to the response time shown.
④ Unlatching occurs 1 millisecond before circuit breaker contacts begin to separate.
⑤ For 1 minute.

Series C External Accessories

Contents

Description	*Page*
Product Overview	**V4-T2-116**
Standards and Certifications	**V4-T2-117**
Quick Reference	**V4-T2-118**
G-Frame (15–100 Amperes)	**V4-T2-121**
F-Frame (10–225 Amperes)	**V4-T2-135**
J-Frame (70–250 Amperes)	**V4-T2-153**
K-Frame (70–400 Amperes)	**V4-T2-161**
L-Frame (125–600 Amperes)	**V4-T2-185**
M-Frame (300–800 Amperes)	**V4-T2-211**
N-Frame (400–1200 Amperes)	**V4-T2-222**
R-Frame (800–2500 Amperes)	**V4-T2-237**
Motor Circuit Protectors (MCP)	**V4-T2-256**
Motor Protection Circuit Breakers (MPCB)	**V4-T2-267**
Type ELC Current Limiter Attachment (Size 0–4)	**V4-T2-269**
Current Limiting Circuit Breaker Module	**V4-T2-270**
Internal Accessories	**V4-T2-273**
External Accessories	
Product Selection	**V4-T2-310**
Accessories	**V4-T2-328**
Technical Data and Specifications	**V4-T2-329**
Dimensions	**V4-T2-330**

External Accessories

Product Overview

End Cap Kit

The end cap kit slides onto the line or load conductor of the circuit breaker and acts as a threaded adapter for the conductor to accept a ring terminal or other bolt-on connector. The end cap kit is available with English and metric thread sizes. (Field installation only.) Listed per UL File E7819.

Keeper Nut

The keeper nut slides onto the line or load conductor of the circuit breaker and acts as a threaded adapter for the conductor to accept a ring terminal or other bolt-on connector. The keeper nut is available with English and metric thread sizes. Screws and washers are supplied by customer. (Field installation only.) Listed per UL File E7819.

L-, M-, N-Frames

Not required. Terminals are threaded.

J-Frame Plug Nut

The plug nut is used in applications where screw-connected ring-type terminals are preferred to connect cables to circuit breaker conductors. The plug nut is press-fit into the opening in the circuit breaker terminal conductor. Screws and washers are supplied by customer.

Terminal Adapter

Control Wire Terminal Kit

The control wire terminal kit provides a means to tap off control power from a main disconnect, using the provided male end of a quick disconnect.

For use with steel or stainless steel terminals only.

Note: Terminal Kits contain one terminal for each pole and one terminal cover.

Multiwire Connectors

Eaton's field-installed multiwire connectors for the load side (OFF) end terminals are used to distribute the load from the circuit breaker to multiple devices without the use of separate distribution terminal blocks.

Multiwire lug kits include mounting hardware, insulators and tin-plated aluminum connectors to replace three mechanical load lugs. UL listed as used on the load side (OFF) end.

Terminal Shields

Terminal shields provide protection against accidental contact with live line side terminations. Terminal shields are fabricated from high dielectric insulating material and fasten over the front terminal access openings. Small openings in the shields provide limited access to the terminals for tightening connectors. (Field installation only.)

Rear Fed Terminals.

Rear fed terminals allow the cable to connect to the breaker from the back instead of the top. Terminal shields or interphase barriers are included with each rear fed terminal kit (depending on frame size). When catalog number starts with a 3, it indicates a kit with three terminals in each kit. Catalog number beginning with a TA indicates one terminal.

Terminal End Covers

The terminal end covers are designed for use in motor control center applications where, because of confined spaces, line side conductors are normally custom fitted. The molded end covers are made of high dielectric glass-polyester and slide over the line ends of the circuit breaker. Close fitting conductor openings are molded into the end covers. The end cover and circuit breaker case fit together to form terminal compartments that isolate discharged ionizing gases during circuit breaker tripping. Terminal end covers are available with two conductor opening diameters, 0.25-inch (6.4 mm) and 0.41-inch (10.4 mm), and are listed per UL File E7819. (Field installation only.)

Interphase Barriers

The interphase barriers provide additional electrical clearance between circuit breaker poles for special termination applications. The barriers are high dielectric insulating plates that are installed in the molded slots between the terminals. (Field installation only.) Two per package.

Base Mounting Plate

Suitable for mounting six single-pole circuit breakers.

DIN Rail Adapter

For use with standard 35 mm DIN rail such as, 35 x 7.5 or 35 x 15 mm per DIN EN50022.

Adapter mounting screws included are for use with two- and three-pole circuit breakers. Adapters for single-pole circuit breakers clip into the base molding.

Key Operated Attachment

Lock Dog (Non-Padlockable)

Non-Padlockable Handle Block

The non-padlockable handle block secures the circuit breaker handle in either the ON or OFF position. (Trip-free operation allows the circuit breaker to trip when the handle block holds the circuit breaker handle in the ON position.) The device is positioned over the circuit breaker handle and secured by a setscrew to deter accidental operation of the circuit breaker handle. Listed per UL File E7819. (Field installation only.)

Padlockable Handle

Padlockable Handle Lock

The device is positioned in the cover opening to prevent handle movement. Will accommodate one 5/16-inch (8 mm) padlock.

Snap-on Padlockable Handle Lock Hasp

The snap-on padlockable handle lock allows the handle to be locked in the OFF or ON position. (Trip-free operation allows the circuit breaker to trip when the handle lock holds the circuit breaker handle in the ON position.) This device was designed for use on the single-pole circuit breaker, but may be used on one-, two-, three- and four-pole styles. The handle lock snaps onto the escutcheon area of the handle with an optional retaining screw for added secureness. The handle lock will accommodate one padlock with a 1/4-inch (6.4 mm) shackle. Listed per UL File E7819. (Field installation only.)

Padlockable Handle Lock Hasp

The padlockable handle lock hasp allows the handle to be locked in the ON or OFF position. (Trip-free operation allows the circuit breaker to trip when the handle lock holds the circuit breaker handle in the ON position.) The hasp mounts on the circuit breaker cover within the trimline. The cover is predrilled on both sides of the operating handle so that the hasp can be mounted on either side of the handle. The hasp will accommodate up to three padlocks with 1/4-inch (6.4 mm) shackles, one per circuit breaker. Listed per UL File E7819. (Field installation only.)

Cylinder Lock

The cylinder lock internally blocks the trip bar in the tripped position to prevent the circuit breaker from being switched to ON. The cylinder lock is factory installed in the left pole only of the circuit breaker cover. Other internally mounted accessories cannot be installed in the same pole as the cylinder lock. (Factory installation only.)

Key Interlock Kit (Lock Not Included)

The key interlock is used to externally lock the circuit breaker handle in the OFF position. When the key interlock is locked, an extended deadbolt blocks movement of the circuit breaker handle. Uniquely coded keys are removable only with the deadbolt extended. Each coded key controls a group of circuit breakers for a given specific customer installation.

The key interlock assembly is Underwriters Laboratories listed for field installation under UL File E7819 and consists of a mounting kit and a purchaser supplied deadbolt lock. The mounting kit comprises a mounting plate, which is secured to the circuit breaker cover in either the left- or right-pole position, key interlock mounting screws, and a wire seal. Specific mounting kits are required for individual key interlock types.

Sliding Bar Interlock

The sliding bar interlock provides mechanical interlocking between two adjacent three-pole circuit breakers. It is installed on the enclosure cover between the circuit breakers. When the sliding bar interlock handle is moved from one side to the other, a bar extends to alternately block movement of the circuit breaker handles and prevents both circuit breakers from being switched to ON at the same time. Sliding bar interlocks are not UL listed. (Field installation only.)

Walking Beam Interlock

The walking beam Interlock provides mechanical interlocking between two adjacent circuit breakers of the same pole configuration. The walking beam interlock mounts on a bracket behind and between the circuit breakers. A plunger on each end of the beam is inserted through an access hole in the back plate and base of each circuit breaker. The walking beam interlock prevents both circuit breakers from being switched ON at the same time. If a walking beam interlock is installed, the wiring troughs in the back of the circuit breaker case are blocked by the plungers and cannot be used for cross wiring. Factory modified circuit breakers are required for this application. UL File E38116.

Electrical Operator

The electrical (solenoid) operator is a single solenoid mechanism that enables local and remote circuit breaker ON, OFF, and reset switching. The electrical operator is mounted on the circuit breaker cover within the trimline of the circuit breaker. The electrical operator uses a unique bi-stable latch that allows the device to operate using one solenoid. The accessory provides high-speed switching with a maximum operating time of 5 cycles (80 mS), making it suitable for generator synchronizing applications.

Means are provided for remote electrical operation and for local manual operation. A special slide includes provisions for padlocking the circuit breaker handle in the OFF position. The slide will accept three padlock shackles with a maximum diameter of 1/4-inch (6.4 mm) each. An interlock electrically disconnects the solenoid when the electrical operator cover is removed. The rating data tables provide electrical rating data for the electrical (solenoid) operator.

The electrical (motor) operator allows the circuit's breaker to be opened, closed or reset remotely. It also has a lock-off capability and provisions for manual operation.

The electrical (motor) operator contains a reversible motor connected to a ball screw. The ball screw drives the circuit breaker handle. Limit switches and relays are used to control the motor.

Plug-In Adapters

Plug-in adapters simplify installation and front removal of circuit breakers. Individual line and load plug-in adapters are available for rear connection applications on two-, three-, and four-pole circuit breakers. Common mounting plates for line- and load-end adapters are available.

One plug-in adapter kit is required for line-end and one for load-end.

Plug-in adapters are UL approved unless otherwise noted.

Rear Connecting Studs

Rear connecting studs are available in several sizes to accommodate specific fixed-mounted circuit breaker applications.

Each rear connecting stud assembly consists of one stud and one tube. To maintain proper clearances between poles, select alternate long and short stud assemblies for circuit breakers with more than one pole. One assembly is required for line-end and one for load-end of each pole. Tubes must be ordered separately. Connecting studs are available only with English thread sizes.

Note: Not UL listed.

Panelboard Connecting Straps

Panelboard connecting straps are used to connect the circuit breaker terminals to the panelboard bus. The panelboard connecting straps are available with various ratings for outside and center poles. (Field installation only.)

Panelboard connecting straps are available to meet the needs of most standard panelboard applications. Style numbers for mounting brackets for CDP panelboard installations are also included.

Note: Not UL listed. Refer to panelboard manufacturer for compatibility.

Type LFD Current Limiter

The LFD current limiter is an accessory that bolts to the load end of a standard FDB or FD thermal-magnetic circuit breaker, providing 200,000 A interrupting capacity at up to 600 Vac. LFD current limiters for thermal-magnetic and electronic circuit breakers are listed with Underwriters Laboratories under File E47239.

Ground Fault Alarm Unit

The ground fault alarm unit is a remotely mounted device with a combination indicating light/test button that will light when the breaker trips or alarms on ground fault. The ground fault alarm unit requires a separate 120 Vac power source to power the light and the internal relay, which has 1NO and 1NC contacts for remote indication. The ground fault alarm unit can be panel mounted for ordering with an optional face mounting bracket. For use on Digitrip 310 only, K- through N-Frame.

IQ Energy Sentinel

The IQ Energy Sentinel is a highly accurate, microprocessor-based, breaker-mounted device designed to monitor power and energy readings. It represents an alternative to watt meters, watt-hour meters, and watt demand meters. Key advantages include savings in space, lower installation costs, and remote monitoring capability.

The IQ Energy Sentinel mounts on the load side of a Series C F-Frame (150 ampere) circuit breaker. It can be applied on three-phase, four-wire systems, or single-phase, three-wire systems with voltage connected through Phases A and C.

For more information, see Descriptive Bulletin 8178.

Potential Transformer Module

The potential transformer module is required for the Digitrip OPTIM 1050 to provide a voltage input to allow the trip unit to monitor power and energy as well as power factor. The potential transformer module is a 6 VA transformer with a primary voltage input of up to 600 volt line to line. Three 0.1 ampere fuses are provided on the primary of the transformer and can be used for isolation purposes during dielectric testing. The device is normally panel mounted and can feed up to 16 OPTIM trip units.

Solid-State (Electronic) Portable Test Kit

The solid-state (electronic) portable test kit provides verification of performance of all ratings of Digitrip 310 electronic trip units installed in circuit breakers while in service under varying load and/or phase imbalance. The test kit operates on 120-volt, 50/60 Hz power; it includes complete instructions and test times for testing long time, short time/instantaneous operation and optional ground fault operation of the circuit breaker.

Breaker Interface Module (BIM)

The Breaker Interface Module (BIM) is a panel mounted user interface device that is mounted on the front of an electrical assembly or at a remote location. The BIM is used to access, configure, test and display information for OPTIM trip units and other devices. The BIM consists of four display windows, eight function buttons, 18 LEDs, and a graphical time/current curve to provide breaker status, operational information, protection status and energy monitoring. A 24 Vdc power supply is required to provide power to the BIM. This is supplied by the switchboard builder to Eaton's specifications. The BIM is a member of Eaton's PowerNet family of communicating devices that connects OPTIM trip units, Digitrip RMS 810/910 trip units and energy sentinels as a subnetwork system. The BIM can also be connected to a main network via a PONI module to PowerNet software.

Digitrip OPTIMizer

The Digitrip OPTIMizer is a hand-held programmer that is used to access, configure, test and display information from OPTIM trip units. The OPTIMizer plugs into the front of an OPTIM trip unit via an eight-pin telephone jack and is powered by a nine-volt battery or the auxiliary power module. One highlighted feature is the "Copy" and "Download" commands.

Setting up multiple OPTIM trips can be finished in minutes and with no errors. An Auxiliary Power Module connection provides a trip test when control power is not present at the breaker. The OPTIMizer is supplied as a standard package to include the programmer, the eight-pin connection cord, battery and carrying case. The auxiliary power module is optional.

Auxiliary Power Module

The auxiliary power module is a power supply requiring 120 Vac input at 50 or 60 Hz that provides a 32 Vdc output. The auxiliary power module provides control power for testing an OPTIM trip unit when other means of control power is not available or for continuous OPTIMizer operation versus temporary with a battery. The auxiliary power module connects into the top of the Digitrip OPTIMizer via a keyed receptacle. The main application for the auxiliary power module would be for the testing of a standalone non-communicating OPTIM breaker that ordinarily would not have control power.

Cause of Trip Display/Remote Mount Cause of Trip Display

The Cause of Trip Display can be field-installed on any Digitrip RMS 310+ trip unit. The device provides breaker information through an LCD screen, such as cause of trip, phrase current, ground current and low loads. The display is ideal for troubleshooting common trips such as ground fault, long delay, and instantaneous/short delay. The DIGIVIEW version will provide a local display at the breaker without additional wiring by connecting directly onto the trip unit. The DIGIVIEWR06 version has a 6 foot cable that allows users to mount the display on the outside of an enclosure door and connect to the trip unit that is contained inside the enclosure.

Cause of Trip LED Module

The Cause of Trip LED Module can be field-installed on any Digitrip RMS 310+ trip unit. The device provides a cause of trip indication via LED. The Cause of Trip LED Module connects directly onto the trip unit. When the breaker trips, the module indicates the cause of trip (long delay, short delay, instantaneous and ground) via LED indication. The module is reset after the breaker is reset.

Note: The OPTIMizer can work off of 32 Vdc control power, although 24 Vdc is the standard on OPTIM breakers.

Product Selection

Termination Hardware—End Cap Kit

End Cap Kit



End Cap Kit

Thread Type	Thread Size	Catalog Number
Two-Pole F-Frame (225A)		
Imperial	10–32	**KPEK12**
Metric	M–5	**KPEKM12**
Three-Pole F-Frame (225A)		
Imperial	10–32	**KPEK1**
Metric	M–5	**KPEKM1**
Four-Pole F-Frame (225A)		
Imperial	10–32	**KPEK14**
Metric	M–5	**KPEKM14**
Three-Pole J-Frame		
Imperial	0.312–18	**KPEK2**
Metric	M–8	**KPEKM2**
Four-Pole J-Frame		
Imperial	0.312–18	**KPEK24**
Metric	M–8	**KPEKM24**
Three-Pole K-Frame		
Imperial	0.312–18	**KPEK3**
Metric	M–8	**KPEKM3**
Four-Pole K-Frame		
Imperial	0.312–18	**KPEK34**
Metric	M–8	**KPEKM34**
Three-Pole L-Frame		
Imperial	0.312-18	**KPEK4**
Metric	M-8	**KPEKM4**
Four-Pole L-Frame		
Imperial	0.312–18	**KPEK44**
Metric	M–8	**KPEKM44**

Termination Hardware—Keeper Nut

F-Frame Keeper Nut



F-Frame Keeper Nut

Thread Type	Thread Size	Catalog Number Package of 12 (Priced Individually)
Imperial	10–32	**KPR1A**
Metric	M–5	**KPR1AM**

K-Frame Keeper Nut



K-Frame Keeper Nut

Thread Type	Thread Size	Line/Load End	Catalog Number Package of 3
Imperial	0.375–16	Line	**KPR3A**
		Load	**KPR3B**
Metric	M–8	Line	**KPR3AM**
		Load	**KPR3BM**

Note

L-, M-, N-Frames not required. Terminals are threaded.

Termination Hardware

J-Frame Plug Nut



J-Frame Plug Nut

Thread Type	Thread Size	Catalog Number Package of 6
Imperial	0.250–20	**PLN2**
Metric	M–6	**PLN2M**

K-Frame Terminal Adapter



K-Frame Terminal Adapter ①

Line/Load End	Catalog Number
Line and load	**TAD3**

F-Frame Ordering Information

Terminals must be ordered separately. Priced individually.

F-Frame Kit



F-Frame Control Wire Terminal Kit ②

Description	Maximum Amperes	Catalog Number
Package of 12 control wire terminal tangs.	150	**FCWTK**
	225	**FCWTK225**

J- and K-Frame Ordering Information

Terminals must be ordered separately. Priced individually.

J- and K-Frame Kit



J- and K-Frame Control Wire Terminal Kit

Description	Catalog Number
Package of 12 control wire terminal tangs.	**KCWTK**

L-Frame Control Wire Terminal Kit

AWG Wire Range/Number Conductors	Metric Wire Range mm²	Catalog Number
Al/Cu 3/0–350 kcmil (2)	95–150	**TA602LDCW** ③
Cu 250–350 kcmil (2)	120–250	**T602LDCW** ③
Al/Cu 400–500 kcmil (2)	185–240	**2TA603LDKCW** ④⑤
Al/Cu 400–500 kcmil (2)	185–240	**3TA603LDKCW** ④⑥
Al/Cu 400–500 kcmil (2)	185–240	**4TA603LDKCW** ④⑦

Notes

① K-Frame terminal adapter for use in replacing LB/DA breakers.
② Not for use with T250KB terminals.
③ Individually packed.
④ Terminal kits contain one terminal for each pole and one terminal cover.
⑤ Two-pole kit.
⑥ Three-pole kit.
⑦ Four-pole kit.

Termination Hardware

G-Frame Control Wire Terminal

Description	Catalog Number	Catalog Number
Control wire terminal (kit of 12)	**5652B38G01**	**GCWTK**

Multiwire Connectors



Multiwire Connectors Ordering Information (Package of 3)

Maximum Amperes	Wires per Terminal	Wire Size Range AWG Cu	Kit Catalog Number ①
G-Frame ②			
100	3	14–2	**3TA100G3K**
	6	14–6	**3TA100G6K**
F-Frame			
225	3	14–2	**3TA150F3K**
	6	14–6	**3TA150F6K**
J-Frame			
250	3	14–2	**3TA250J3K**
	6	14–6	**3TA250J6K**
K-Frame			
400	3	14–2/0	**3TA400K3K**
	6	14–3	**3TA400K6K**

Rear Fed Terminals

Frame	Maximum Amperes	Wire Size Range AWG Cu	Catalog Number ①
FD	150	14–4/0	**TA150FDRF**
	150	14–4/0	**3TA150FDRF**
	225	6–300 kcmil	**TA225FDRF**
	225	6–300 kcmil	**3TA225FDRF**
KD	400	250–500 kcmil	**TA350KRF**
	400	250–500 kcmil	**3TA350KRF**
MDL	800	3/0 MAX (3)	**TA800MDLRF**
	800	3/0 MAX (3)	**3TA800MDLRF**

Base Mounting Hardware

Ordering Information

Hardware for surface mounting of circuit breakers is supplied only on request. Hardware consists of mounting screws and lockwashers. Order hardware for circuit breaker pole configurations as required.

Mounting Hardware

Screw Length in Inches (mm)	Catalog Number
G-Frame	
0.138–32 x 2.63 (3.5 x 66.7 mm) Std.	**624B375G23**
0.138–32 x 3.00 (3.5 x 76.2 mm)	**8703C80G05**

Notes

① When catalog number starts with a 3, it indicates a kit with three terminals in each kit. Catalog number beginning with a TA indicates one terminal.

② GD breakers require special tapping for multiwire lugs, as described in the IL or use with standard aluminum collars.

Imperial Thread Mounting Hardware

Number of Poles	Description	Type of Mounting	Catalog Number
F-Frame			
1	0.164-32 x 3.188-inch pan-head steel screws, lockwashers and clamps	Individual	**624B375G01**
		Group ①	**624B375G02**
2	0.164-32 x 1.5-inch pan-head steel screws and lockwashers	Individual	**4218B80G01**
3, 4	0.164-32 x 1.5-inch pan-head steel screws and lockwashers	Individual	**BMH1**
J-Frame			
2, 3, 4	0.250-20 x 2.75 inch pan-head steel screws and lockwashers	Individual	**BMH2**
K-Frame			
2, 3, 4	0.250-20 x 1.5 inch pan-head steel screws and lockwashers	Individual	**BMH3**
L-Frame			
2, 3, 4	0.250-20 x 1.5 inch filister-head steel screws and lockwashers and flat washers	Individual	**BMH4**
M-Frame			
2, 3	0.3125-18 x 1.25 inch filister-head steel screws and lockwashers and flat washers	Individual	**BMH5**
N-Frame			
2, 3, 4	0.3125-18 x 1.25 inch pan-head steel screws and lockwashers	Individual	**BMH5**
R-Frame			
Supplied by customer			

Metric Thread Mounting Hardware

Number of Poles	Description	Type of Mounting	Catalog Number
F-Frame			
1	M4–0.7 x 80 mm pan-head steel screws, lockwashers, and clamps	Individual	**4218B80G09**
		Group ①	**4218B80G10**
2	M4–0.7 x 38 mm pan-head steel screws and lockwashers	Individual	**4218B80G11**
3, 4	M4–0.7 x 38 mm pan-head steel screws and lockwashers	Individual	**BMH1M**
J-Frame			
2, 3, 4	M6–0.7 x 70 mm pan-head steel screws and lockwashers	Individual	**BMH2M**
K-Frame			
2, 3, 4	M6–0.7 x 38 mm pan-head steel screws and lockwashers	Individual	**BMH3M**
L-Frame			
2, 3	—	Individual	**BMH4M**
M-Frame			
2, 3	—	Individual	**BMH4M**
N-Frame			
2, 3	—	Individual	**BMH5M**
R-Frame			
Supplied by customer			

Note

① One set of hardware for two circuit breakers.

Terminal Shields

2

G-Frame Terminal Shield

Number Units in Package	Catalog Number
10	**GTSK3**

F-Frame

F-Frame Terminal Shield

Number of Poles	Location	Standard (Package of 10) (Priced Individually) Catalog Number	Special—For Use When Electrical Operator is Mounted on Circuit Breaker Catalog Number
1	Line	**625B229G06**	—
2	Line	**625B229G07**	—
3	Line	**625B229G08**	**4210B95G01**
4	Line	**625B229G09**	**4210B95G02**

J-Frame

J-Frame Terminal Shield

Number of Poles	Location	Catalog Number (Package of 10)
2, 3	Line End	**1266C07G01**
4	Line End	**6631C01G01**
2, 3	Load End	**6641C16G01**
4	Load End	**6641C16G02**

K-Frame

K-Frame Terminal Shield

Number of Poles	Location	Catalog Number (Package of 10)
2, 3	Line	**TS33LN**
4	Line	**TS34LN**
3	Load	**TS33LD**

L-Frame Terminal Shield

Catalog Number (Package of 1)
314C420G05

M-Frame Terminal Shield

Catalog Number (Package of 1)
208B966G01

N-Frame Terminal Shield

Catalog Number (Package of 1)
NTS3K

Terminal End Covers

Ordering Information

The terminal end cover is available for three-pole circuit breakers only. Two conductor opening sizes are available. Specify quantity (one per circuit breaker) when ordering.

F-Frame

F-Frame Terminal End Covers

Conductor Opening Diameter in Inches (mm)	Catalog Number
0.25 (6.35 mm)	**TEC1**
0.41 (10.41 mm)	**TEC2**

Interphase Barriers

Ordering Information

Two per package.

Interphase Barrier

Interphase Barriers

Frame	Catalog Number
F	**IPB1**
J, K	**IPB3**
L	**IPB4**
M	**IPB4**
N	**IPB5**

Base Mounting Plate

Base Mounting Plate

Base Mounting Plate G-Frame GD/GHC

Number of Units in Package	Catalog Number
1	**207B513G01**

DIN Rail Adapter

DIN Rail Adapter

DIN Rail Adapter G-Frame GD/GHC

Number of Poles	Number of Units in Package	Catalog Number
1, 2	10	**1225C79G01**
3	10	**1225C79G02** ①

All Metal DIN Rail Adapter G-Frame GD/GHC

Number of Poles	Number of Units in Package	Catalog Number
3	1	**EGGDDIN**

Key Operated Attachment

Key Operated Attachment



Key Operated Attachment G-Frame GD/GHC

Number of Units in Package	Catalog Number
10	**GKOA**

Note

① For use on three-pole breakers only.

2

Lock Dog (Non-Padlockable)

Lock Dog (Non-Padlockable)

Lock Dog (Non-Padlockable) G-Frame GD/GHC/GHB/GMCP

Number of Units in Package	Catalog Number
1	**1294C01H01**

Handle Ties

Handle Tie—Series C, F-Frame

Number of Poles	Number of Units in Package	Catalog Number
2	10	**HTBFD2P**
3	10	**HTBFD3P**

Handle Tie—Series C, G-Frame

Number of Poles	Number of Units in Package	Catalog Number
2	10	**HTBGD2P**
3	10	**HTBGD3P**

Non-Padlockable Handle Block

Non-Padlockable Handle Block

Non-Padlockable Handle Block

Frame	Catalog Number
F	**LKD1**
J, K	**LKD3**
L, M, N	**LKD4**

Padlockable Handle

Padlockable Handle

Padlockable G-Frame GD/GHC/GHB

Number of Units in Package	Catalog Number ①
10	**1223C77G03**
10	**1223C77G05** ②
10	**1223C77G06** ②

Padlockable Handle Lock

Padlockable Handle Lock

Padlockable Handle Lock

Frame	Catalog Number
G	**GPHBOFF**
J, K	**PHB3**

Snap-On Padlockable Handle Lock Hasp

Snap-On Padlockable Handle Lock Hasp

Snap-On Padlockable Handle Lock Hasp

Frame	Catalog Number
F	**PHL1**

Notes

① Accepts 0.285 Lock Shank.

② Padlockable in the OFF position only.

Padlockable Handle Lock Hasp

Padlockable Handle Lock Hasp

Padlockable Handle Lock Hasp

Description	Catalog Number
F-Frame	
Single-pole breakers	**PHL1**
Two-, three- and four-pole breakers	**PLK1**
For left side mounting	**PLK1LOFF**
For right side mounting	**PLK1ROFF**
J, K-Frames	
Two-, three- and four-pole breakers	**PLK3**
For left side mounting	**PLK3LOFF** ①
For right side mounting	**PLK3ROFF** ①
L-Frame (Side Mounted)	
Lock ON or OFF	**HLK4**
Lock OFF only (left-hand mount)	**HLK4LOFF** ①
L-Frame (Top Mounted)	
Lock ON or OFF	**HLK4S**
Lock OFF only	**HLK4SOFF** ①
M-Frame	
Lock ON or OFF	**HLK4**
Lock OFF only (left-hand mount)	**HLK4LOFF** ①
M-Frame (Vertical Mounting)	
Lock ON/OFF	**HLK4S**
Lock OFF only	**HLK4SOFF**
N-Frame	
Side mounted	**PLK5**
Top mounted (ON/OFF)	**PLK5S**
Top mounted (OFF only)	**PLK5SOFF** ①
R-Frame	
Lock ON/OFF	**HLK6**
Lock OFF only	**HLK6OFF** ①

Cylinder Lock

Cylinder Lock

Cylinder Lock

Frame	Catalog Number
F, J, K	Order by description

Note

① For padlockable handle lock hasp to padlock handle in OFF position only, order either catalog number.

Key Interlock Kit

Ordering Information

2

Key interlock kits contain the necessary interface and hardware to install a trapped key interlock from one of the listed manufacturers. Key interlocks are not installed or supplied as part of the breaker, and must be obtained separately from the lock manufacturer or through the manufacturer of the equipment on which the breaker will be installed. Select the mounting kit catalog number to match the type of lock used.

Key Interlock Kit

Key Interlock Kit (Trapped Key Interlock)

Lock Manufacturer	Lock Type	Bolt Projection in Withdrawn Position in Inches (mm)	Kit Catalog Number
F-Frame			
Superior	B-4003-1	0.38 (9.5)	**KYK1**
Kirk®	F	0.38 (9.5)	**KYK1**
Castell ①	K or QK	0.38 (9.5)	**CTK1**
J, K-Frames			
Superior	B-4003-1	0.38 (9.5)	**KYK3**
Kirk	F	0.38 (9.5)	**KYK3**
Castell ①	K or QK	0.38 (9.5)	**CTK3**
L-, M-, N-Frames			
Superior	B-4003-1	0.38 (9.5)	**KYK4**
Kirk	F	0.38 (9.5)	**KYK4**
Castell ①	K or QK	0.38 (9.5)	**CTK4**
R-Frame			
Superior	B-4003-1	1.0 (25.4)	**KYK6**
Kirk	F	1.0 (25.4)	**KYK6**
Castell ①	K or QK	1.0 (25.4)	**CTK6**
JG-Frame			
Superior	B-4003-1	0.38 (9.5)	**KYKJG**
Kirk	F	0.38 (9.5)	**KYKJG**
Castell ①	K or QK	0.38 (9.5)	**CTKJG**
LG-Frame			
Superior	B-4003-1	0.38 (9.5)	**KYKLG**
Kirk	F	0.38 (9.5)	**KYKLG**
Castell ①	K or QK	0.38 (9.5)	**CTKLG**

Note

① When ordering Castell Interlock, it is necessary for customer to specify that the mounting bolt holes must be 10 mm in diameter

Sliding Bar Interlock

Ordering Information

The sliding bar interlock is available for mounting between two adjacent three-pole circuit breakers with circuit breakers centerline spacing as indicated in table and enclosure front panel thickness of 1/8 or 3/16 inch (3.2 or 4.8 mm). (For field installation only.)

Sliding Bar Interlock

Sliding Bar Interlock

Frame	Centerline Spacing in Inches (mm)	Catalog Number
F	4.19 (106.4)	**SBK1**
J	4.38 (111.3)	**SBK2**
K	5.75 (146.0)	**SBK3**
L, M	8.50 (215.9)	**SBK4**
N	8.50 (215.9)	**SBK5**

Walking Beam Interlock

Ordering Information

The walking beam interlock is available for mounting between two adjacent circuit breakers spaced 1/4-inch (6.4 mm) apart and having the same pole configuration. The two circuit breakers must be factory modified to accept the walking beam interlock assembly (suitable for use with either two-, three- or four-pole circuit breakers).

With properly modified circuit breakers, the walking beam interlock is suitable for field installation. Order circuit breakers specifying modification for walking beam (20% price adder) and select walking beam interlock from table below. Circuit breakers and walking beam interlock are boxed and shipped separately.

Walking Beam Interlock

Walking Beam Interlock

Frame	Catalog Number
F	**WBL1**
K	**WBL3**
L, M	**WBL4A**
N	**WBL5**
R ①	**WBL6**

Note

① Three-pole only.

Electrical Operator

F-Frame Electrical (Solenoid) Operator

Voltage	Frequency	Terminal Block Catalog Number	18-Inch (457.2 mm) Pigtail Lead Catalog Number
120	AC	**EOP1T07**	**EOP1P07**
240	AC	**EOP1T11**	**EOP1P11**

F-Frame Electrical (Motor) Operator ①

Voltage	Frequency	18-Inch (457.2 mm) Pigtail Lead Catalog Number
120	50/60 Hz AC	**MOPFD120C**
24	DC	**MOPFD24D**
125	DC	**MOPFD120C**
208–240	50/60 Hz	**MOPFD240C**
220–250	DC	**MOPFD240C**

J-Frame Electrical (Solenoid) Operator

Operating Voltage	Frequency	Terminal Block Catalog Number
120	50/60 Hz AC	**EOP2T07**
240	50/60 Hz AC	**EOP2T11**

K-Frame Electrical (Solenoid) Operator

Operating Voltage	Frequency	Terminal Block Catalog Number
120	50/60 Hz AC	**EOP3MT07**
240	50/60 Hz AC	**EOP3MT11**

K-Frame Electrical (Solenoid) Operator Base Mounting Kit

Frame	Catalog Number
K	**BBMK3**

L- and M-Frame Electrical (Motor) Operator (310 and OPTIM)

Operating Voltage	Frequency	Terminal Block Catalog Number
120	50/60 Hz	**EOP4MT07**
208	50/60 Hz	**EOP4MT11**
240	50/60 Hz	**EOP4MT11A**
480	50/60 Hz	**EOP4MT15**
125	DC	**EOP4MT26**
24	DC	**EOP4MT21**

Note

① Motor operators MOP1P07, MOP1P03DC, MOP1P05DC and MOP1P07DC are replaced by MOPFD motor operators listed in table.

N-Frame Electrical (Motor) Operator

Operating Voltage	Frequency	Pigtail Leads Catalog Number
120	50/60 Hz	**EOP5T07**
208	50/60 Hz	**EOP5T09**
240	50/60 Hz	**EOP5T11**
480	50/60 Hz	**EOP5T15**
24	DC	**EOP5T21**
48	DC	**EOP5T22**
125	DC	**EOP5T26**

R-Frame Electrical (Motor) Operator

Operating Voltage	Frequency	Factory-Installed Terminal Block Catalog Number
120	50/60 Hz	**EOP6T08K**
240	50/60 Hz	**EOP6T11K**
48	DC	**EOP6T21K**

Plug-In Adapters

F-Frame Ordering Information (Flat Bar Type)

Continuous Current Rating (Amperes)	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole Catalog Number
100–225	**1480D13G01**	**1480D13G02**	**1480D13G07** ①
Mounting plate	**176C511H01**	**507C047H01**	—

J-Frame Ordering Information (Flat Bar Type)

Continuous Current Rating (Amperes)	Terminal End	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole Catalog Number
250	Line	**1260C86G05**	**1260C86G06**	**1231C67G01**
	Load	**1260C86G07**	**1260C86G08**	**1231C67G02**
	One line and one load	**506C144G27**	**506C144G28**	—
Mounting plate	—	②	**PMP23**	—

K-Frame Ordering Information (Flat Bar Type)—600 Vac Maximum

Continuous Current Rating (Amperes)	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole Catalog Number
400	**PAD32**	**PAD33**	—
Mounting plate	②	**PMP33**	—

Notes

① 100 ampere maximum.

② Use three-pole mounting plate for two-pole circuit breaker.

L-Frame (Threaded Stud Type)

Continuous Current Rating (Amperes)	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole Catalog Number
600 (threaded stud type)	**506C059G03**	**506C059G04**	**PAD44**
600 (flat bar type)	**1288C19G01**	**1288C19G02**	**6636C55H01**
Mounting plate	**504C824H01**	**504C824H01**	—

M-Frame (Flat Bar Type)—600 Vac Maximum

Continuous Current Rating (Amperes)	Two-Pole Catalog Number	Three-Pole Catalog Number
800	**2614D53G05**	**2614D53G06**
Mounting plate	**1290C73H01**	**1290C73H01**

N-Frame (Flat Bar Type)

Continuous Current Rating (Amperes)	Two-Pole Catalog Number	Three-Pole Catalog Number
1200	**2614D53G03**	**2614D53G04**
Mounting plate	**1290C73H01**	**1290C73H01**

Plug-In Adapters

Frame	Number of Poles	Standard Certification	Catalog Number
FD	3	IEC	**PAD3F**
FD	4	IEC	**PAD4F**
JD	3	IEC	**PAD3JD**
KD	3	IEC	**PAD3K**
LD	3	IEC	**PAD3LD**
LD	4	IEC	**PAD4LD**

Rear Connecting Studs

F-Frame ①

Stud Ampere Rating	Stud Catalog Number	Tube Catalog Number
For 15 to 100 Ampere Circuit Breakers		
100 A short	**451D874G01**	**32B9446H20**
100 A short	**451D874G01**	**32B9446H21**
100 A short	**451D874G01**	**32B9446H22**
100 A short	**451D874G01**	**32B9446H23**
100 A long	**451D874G02**	**32B9446H24**
100 A long	**451D874G02**	**32B9446H25**
100 A long	**451D874G02**	**32B9446H26**
100 A long	**451D874G02**	**32B9446H27**
For 110 to 225 Ampere Circuit Breakers		
225A short	**374D883G01**	**374D883H06**
225A short	**374D883G01**	**374D883H07**
225A short	**374D883G01**	**374D883H08**
225A short	**374D883G01**	**374D883H09**
225A long	**374D883G02**	**374D883H10**
225A long	**374D883G02**	**374D883H11**
225A long	**374D883G02**	**374D883H12**
225A long	**374D883G02**	**374D883H13**

J-Frame ①

Stud Ampere Rating	Stud Catalog Number	Tube Catalog Number
250A short	**5010D23G01**	**456D983H05**
250A short	**5010D23G01**	**456D983H06**
250A short	**5010D23G01**	**456D983H07**
250A long	**5010D23G02**	**5010D23H05**
250A long	**5010D23G02**	**5010D23H06**
250A long	**5010D23G02**	**5010D23H07**

K-Frame ①

Stud Ampere Rating	Stud Catalog Number	Standard Tube Catalog Number
400 A short	**6642C14G02**	**313C909H17**
400 A short	**6642C14G04**	**313C909H18**
400 A short	**6642C14G06**	**313C909H19**
400 A long	**6642C14G03**	**313C909H20**
400 A long	**6642C14G05**	**313C909H21**
400 A long	**6642C14G07**	**313C909H22**

L-Frame Ordering Information

Stud Catalog Number
314C960G07
314C960G08
314C960G09

M-Frame Ordering Information ①

Stud Ampere Rating	Stud Catalog Number
225	**314C960G01**
400	**314C960G04**
400	**314C960G05**
400	**314C960G06**
600	**314C960G07**
600	**314C960G08**
600	**314C960G09**
800	**314C960G10**
800	**314C960G11**
800	**314C960G12**

N-Frame Ordering Information ①

Stud Ampere Rating	Stud Catalog Number
800	**623B222G01**
800	**623B222G02**
800	**623B222G03**
1200	**373B375G04**
1200	**373B375G03**

Note

① Not UL listed.

Panelboard Connecting Straps

F-Frame Panelboard Connecting Straps

Bus Spacing in Inches (mm)	Continuous Current Rating (Amperes)	Pole Connector Type Center Catalog Number	Pole Connector Type Outside Catalog Number
2.75 (69.9)	50	**673B142G02**	**673B142G09**
2.75 (69.9)	100	**673B142G02**	**673B142G10**
2.75 (69.9)	150	**673B142G04**	**673B142G03**
3.50 (88.9)	50	**1253C72G01**	**1253C72G03**
3.50 (88.9)	100	**1253C73G03**	**1253C73G06**
3.50 (88.9)	150	**1253C73G01**	**1253C73G05**

F-Frame Mounting Bracket

Number of Poles	Catalog Number
2	**624B600H02**
3	**624B600H01**

J-Frame Panelboard Connecting Straps

Bus Spacing in Inches (mm)	Continuous Current Rating (Amperes)	Pole Connector Type Center Catalog Number	Pole Connector Type Outside Catalog Number
3.50 (88.9)	250	**2600D26G01**	**2600D26G02**

K-Frame Panelboard Connecting Straps

Bus Spacing in Inches (mm)	Continuous Current Rating (Amperes)	Pole Connector Type Center Catalog Number	Pole Connector Type Outside Catalog Number
3.50 (88.9)	400	**4212B78G02**	**4212B77G01**

K-Frame Mounting Bracket

Number of Poles	Catalog Number
2, 3	**208B264H01**

L-Frame Panelboard Connecting Straps

Continuous Current Rating (Amperes)	Pole Connector Type	
	Center Catalog Number	Outside Catalog Number
600	**624B609G01**	**506C052G01**

L-Frame Mounting Bracket

Number of Poles	Catalog Number
2, 3	**208B297H01**

M-Frame Panelboard Connecting Straps

Bus Spacing in Inches (mm)	Continuous Current Rating (Amperes)		Pole Connector Type
		Connector Type	Catalog Number
3.50 (88.9)	800	Short	**314C996G01**
		Medium	**314C996G02**
		Long	**314C996G03**

M-Frame Mounting Bracket

Catalog Number
315C270H01

N-Frame Panelboard Connecting Straps

Bus Spacing in Inches (mm)	Continuous Current Rating (Amperes)		Pole Connector Type
		Connector Type	Catalog Number
3.50 (88.9)	1200	Short	**505C606G04**
		Medium	**505C606G05**
		Long	**505C606G06**

N-Frame Mounting Bracket (Four Required)

Catalog Number
315C270H01

2

Type LFD Current Limiter

The LFD current limiter is an accessory that bolts to the load end of a standard FDB or FD thermal-magnetic and electronic circuit breaker, providing 200,000 A interrupting capacity at up to 600 Vac. LFD current limiters for thermal-magnetic circuit breakers are listed with Underwriters Laboratories under File E47239.

Type LFD Current Limiter

Type LFD Current Limiter

Circuit Breaker Rating Amperes	Catalog Number
15–70	**LFD3070R**
80–160	**LFD3150R**

Ground Fault Alarm Unit

The ground fault alarm unit is a remotely mounted device with a combination indicating light/test button that will light when the breaker trips or alarms on ground fault. The ground fault alarm unit requires a separate 120 Vac power source to power the light and the internal relay, which has 1NO and 1NC contacts for remote indication. The ground fault alarm unit can be panel mounted for ordering with an optional face mounting bracket. For use on Digitrip 310 only, K- through N-Frame.

Ground Fault Alarm Unit

GF Alarm Unit

Description	Catalog Number
Ground fault alarm unit	**GFAU**
Face mounting bracket	**1264C67G01**

IQ Energy Sentinel

The IQ Energy Sentinel is a highly accurate, microprocessor-based, breaker-mounted device designed to monitor power and energy readings. It represents an alternative to watt meters, watt-hour meters, and watt demand meters. Key advantages include savings in space, lower installation costs, and remote monitoring capability.

The IQ Energy Sentinel mounts on the load side of a Series C F-Frame (150 ampere) circuit breaker. It can be applied on three-phase, four-wire systems, or single-phase, three-wire systems with voltage connected through Phases A and C.

For more information, see Descriptive Bulletin 8178.

Potential Transformer Module

The potential transformer module is required for the Digitrip OPTIM 1050 to provide a voltage input to allow the trip unit to monitor power and energy as well as power factor. The potential transformer module is a 6 VA transformer with a primary voltage input of up to 600 volt line to line. Three 0.1 ampere fuses are provided on the primary of the transformer and can be used for isolation purposes during dielectric testing. The device is normally panel mounted and can feed up to 16 OPTIM trip units.

Potential Transformer Module

Potential Transformer Module

Description	Catalog Number
Potential transformer module	**DOPTMLN**

Solid-State (Electronic) Portable Test Kit

The solid-state (electronic) portable test kit provides verification of performance of all ratings of Digitrip 310 electronic trip units installed in circuit breakers while in service under varying load and/or phase imbalance. The test kit operates on 120-volt, 50/60 Hz power; it includes complete instructions and test times for testing long time, short time/instantaneous operation and optional ground fault operation of the circuit breaker.

Portable Test Kit

Description	Catalog Number
Solid-state (electronic) portable test kit	**STK2**

Breaker Interface Module (BIM)

The Breaker Interface Module (BIM) is a panel mounted user interface device that is mounted on the front of an electrical assembly or at a remote location. The BIM is used to access, configure, test and display information for OPTIM trip units and other devices. The BIM consists of four display windows, eight function buttons, 18 LEDs, and a graphical time/current curve to provide breaker status, operational information, protection status and energy monitoring. A 24 Vdc power supply is required to provide power to the BIM. This is supplied by the switchboard builder to Eaton's specifications. The BIM is a member of Eaton's PowerNet family of communicating devices that connects OPTIM trip units, Digitrip RMS 810/910 trip units and energy sentinels as a subnetwork system. The BIM can also be connected to a main network via a PONI module to PowerNet software.

Breaker Interface Module (BIM)

Breaker Interface Module (BIM)

Catalog Number
BIMII

Digitrip OPTIMizer

The Digitrip OPTIMizer is a hand-held programmer that is used to access, configure, test and display information from OPTIM trip units. The OPTIMizer plugs into the front of an OPTIM trip unit via an eight-pin telephone jack and is powered by a nine-volt battery or the auxiliary power module. One highlighted feature is the "Copy" and "Download" commands.

Setting up multiple OPTIM trips can be finished in minutes and with no errors. An Auxiliary Power Module connection provides a trip test when control power is not present at the breaker. The OPTIMizer is supplied as a standard package to include the programmer, the eight-pin connection cord, battery and carrying case. The auxiliary power module is optional.

Note: 24 Vdc Power Supply
A 24 Vdc power supply is required for all Digitrip OPTIM trip units that are required to communicate either on the main Eaton PowerNet network or as a subnetwork to a BIM. The breaker's load is 45 mA of current. Typically one power supply is required per switchboard and can provide control power to a BIM and the OPTIM trip units. The 24 Vdc power supply should be an "isolated high quality" power supply with a "CE" label, and is normally provided by the switchboard manufacturer to Eaton's recommendations.

Digitrip OPTIMizer

Digitrip OPTIMizer

Catalog Number
OPTIMizer—standard package

Auxiliary Power Module

The auxiliary power module is a power supply requiring 120 Vac input at 50 or 60 Hz that provides a 32 Vdc output. The auxiliary power module provides control power for testing an OPTIM trip unit when other means of control power is not available or for continuous OPTIMizer operation versus temporary with a battery. The auxiliary power module connects into the top of the Digitrip OPTIMizer via a keyed receptacle. The main application for the auxiliary power module would be for the testing of a standalone non-communicating OPTIM breaker that ordinarily would not have control power.

Auxiliary Power Module

Auxiliary Power Module

Catalog Number
PRTBAPMDV

Cause of Trip Display/Remote Mount Cause of Trip Display

The Cause of Trip Display can be field-installed on any Digitrip RMS 310+ trip unit. The device provides breaker information through an LCD screen, such as cause of trip, phrase current, ground current and low loads. The display is ideal for troubleshooting common trips such as ground fault, long delay, and instantaneous/short delay. The DIGIVIEW version will provide a local display at the breaker without additional wiring by connecting directly onto the trip unit. The DIGIVIEWR06 version has a 6 foot cable that allows users to mount the display on the outside of an enclosure door and connect to the trip unit that is contained inside the enclosure.

Cause of Trip Display/Remote Mount Cause of Trip Display

Catalog Number
DIGIVIEW
DIGIVIEWR06

Cause of Trip LED Module

The Cause of Trip LED Module can be field-installed on any Digitrip RMS 310+ trip unit. The device provides a cause of trip indication via LED. The Cause of Trip LED Module connects directly onto the trip unit. When the breaker trips, the module indicates the cause of trip (long delay, short delay, instantaneous and ground) via LED indication. The module is reset after the breaker is reset.

Cause of Trip LED Module

Catalog Number
TRIP-LED

Accessories

Flex Shaft Accessories (F- through R-Frame)

NEMA 12 Safety Door Hardware for Flex Shaft and C371 ①

Handle Length in Inches (mm)	Catalog Number ②
4 (101.6)	**C361KJ4**
6 (152.4)	**C361KJ6**
Roller Latch ③	**C361KR**

Series C Rotary Accessories

As an option, an auxiliary switch is offered so that the control panel builder may electrically indicate the status of the breaker.

This accessory would be mounted on the mechanism and comes with 24-inch (609.6 mm) pigtail leads.

Series C Auxiliary Switch

Catalog Number
5108A61G01

Wire Seal

The wire seal can be used to secure the cover on the trip unit to prevent adjustments after settings are confirmed.

Wire Seal

Description	Catalog Number
Wire seal	**5108A03H01**

Notes

① Customer: Consult with box manufacturer for correct door hardware and any adapters required for assembly.

② The 1/4-inch x 1/2-inch (6.35 x 12.7 mm) standard mill rectangular locking bar is not supplied with these kits.

③ Third roller latch for use with 4- or 6-inch (101.6 or 152.4 mm) handle when 3 point latching is required.

Technical Data and Specifications

Electrical Operator

F-Frame Electrical (Solenoid) Operator Rating Data ①②

Voltage ③	Frequency	Inrush Current Amperes	Maximum Operating Time	Fuse Amperes ④
120	50/60 Hz AC	10	5 cycles (80 ms)	3
240	50/60 Hz AC	5	5 cycles (80 ms)	2

F-Frame Electrical (Motor) Operator Rating Data ②⑤⑥⑦

Voltage ③	Frequency	Inrush Current Amperes
120	AC	2
24	DC	5
48	DC	3
125	DC	2

J-Frame Electrical (Solenoid) Operator Rating Data ①⑥⑧⑨

Voltage ③	Inrush Current Amperes	Fuse Amperes
120	30	6
240	16	4

K-Frame Electrical (Solenoid) Operator Rating Data ①⑥⑧⑨

Operating Voltage ③	Inrush Current Amperes	Fuse Amperes
120	30	6
240	16	4

L- and M-Frame Electrical (Motor) Operator Rating Data ①⑥⑧⑩

Operating Voltage ③	Inrush Current Amperes
120 AC	31
208 AC	13
240 AC	12
125 DC	21
24 DC	50

N-Frame Electrical (Motor) Operator Rating Data ①⑥⑪⑫

Operating Voltage ③	Frequency	Inrush Current Amperes	Fuse Amperes
120	50/60 Hz	31	6
208	50/60 Hz	21	—
240	50/60 Hz	19	4
480	50/60 Hz	—	—
24	DC	50	—
48	DC	80	—
125	DC	21	—

R-Frame Electrical (Motor) Operator Rating Data ⑬⑭⑮⑯

Operating Voltage ⑰	Frequency	Motor Inrush Current Amperes
120	50/60 Hz	40
240	50/60 Hz	27
48	DC	53
24	DC	58

Notes

① UL listed under UL File E64983.
② The electrical operator design is endurance tested for 8000 electrical operations.
③ Tolerance: +10%, –15% of nominal voltage.
④ Use current-limiting type fuse where required.
⑤ UL listed under UL File E64124.
⑥ Frequency: 50/60 Hz.
⑦ Maximum operating time: 3 seconds max. Operator is an intermittent duty device. The safe duty cycle (OFF to ON to OFF) should not exceed one per minute.
⑧ The electrical operator design has been endurance tested for 6000 electrical operations.
⑨ Maximum operating time: 5 cycles (80 mS).
⑩ Maximum operating time: 12 cycles.
⑪ The electrical operator design has been endurance tested for 2,500 electrical operations.
⑫ Maximum operating time: 12 cycles max. Operator is an intermittent duty device. The safe duty cycle (OFF to ON to OFF) should not exceed one per minute.
⑬ Operator is an intermittent duty service. The safe duty cycle (OFF to ON to OFF) should not exceed one per minute.
⑭ Electric Operating time at rated voltage; (a) To turn breaker ON–1/2 second max. (b) To turn breaker OFF–1/2 second max.
⑮ Motor operating temperature; Class "A" temperature limits apply.
⑯ A minimum 1 kVA power source is recommended for motor operation.
⑰ Applied voltage should be no less than 85% or no more than 110% of rated voltage.

For OPTIM trip, OPEOPCK kit required.

Dimensions

Approximate Dimensions in Inches (mm)

2

Rear Connecting Studs

F-Frame ①

Stud Ampere Rating	Stud Catalog Number	Panel Thickness A	Tube Length B	C	Tube Catalog Number	Dimensions D	E	F
For 15 to 100 Ampere Circuit Breakers								
100 A short	**451D874G01**	1.00 (25.4)	1.06 (26.9)	—	**32B9446H20**	—	3.63 (92.1)	0.31 (7.9)–18
100 A short	**451D874G01**	0.69–0.94 (17.5 to 23.8)	1.38 (34.9)	—	**32B9446H21**	—	3.63 (92.1)	0.31 (7.9)–18
100 A short	**451D874G01**	0.38–0.63 (9.5 to 15.9)	1.69 (42.9)	—	**32B9446H22**	—	3.63 (92.1)	0.31 (7.9)–18
100 A short	**451D874G01**	0.25–0.31 (6.4 to 7.9)	2.00 (50.8)	—	**32B9446H23**	—	3.63 (92.1)	0.31 (7.9)–18
100 A long	**451D874G02**	1.00 (25.4)	—	3.44 (87.3)	**32B9446H24**	6.13 (155.6)	—	0.31 (7.9)–18
100 A long	**451D874G02**	0.69–0.94 (17.5 to 23.8)	—	3.75 (95.2)	**32B9446H25**	6.13 (155.6)	—	0.31 (7.9)–18
100 A long	**451D874G02**	0.38–0.63 (9.5 to 15.9)	—	4.06 (103.1)	**32B9446H26**	6.13 (155.6)	—	0.31 (7.9)–18
100 A long	**451D874G02**	0.25–0.31 (6.4 to 7.9)	—	4.38 (111.3)	**32B9446H27**	6.13 (155.6)	—	0.31 (7.9)–18
For 110 to 225 Ampere Circuit Breakers								
225A short	**374D883G01**	1.00 (25.4)	1.06 (26.9)	—	**374D883H06**	—	4.25 (108.0)	0.44 (11.1)–14
225A short	**374D883G01**	0.69–0.94 (17.5 to 23.8)	1.38 (34.9)	—	**374D883H07**	—	4.25 (108.0)	0.44 (11.1)–14
225A short	**374D883G01**	0.38–0.63 (9.5 to 15.9)	1.69 (42.9)	—	**374D883H08**	—	4.25 (108.0)	0.44 (11.1)–14
225A short	**374D883G01**	0.25–0.31 (6.4 to 7.9)	2.00 (50.8)	—	**374D883H09**	—	4.25 (108.0)	0.44 (11.1)–14
225A long	**374D883G02**	1.00 (25.4)	—	3.44 (87.3)	**374D883H10**	7.50 (190.5)	—	0.44 (11.1)–14
225A long	**374D883G02**	0.69–0.94 (17.5 to 23.8)	—	3.75 (95.2)	**374D883H11**	7.50 (190.5)	—	0.44 (11.1)–14
225A long	**374D883G02**	0.38–0.63 (9.5 to 15.9)	—	4.06 (103.1)	**374D883H12**	7.50 (190.5)	—	0.44 (11.1)–14
225A long	**374D883G02**	0.25–0.31 (6.4 to 7.9)	—	4.38 (111.3)	**374D883H13**	7.50 (190.5)	—	0.44 (11.1)–14

F-Frame



Note

① Not UL listed.

Approximate Dimensions in Inches (mm)

J-Frame

Stud Ampere Rating	Stud Catalog Number	Panel Thickness A	Tube Length B	C	Tube Catalog Number
250A short	**5010D23G01**	0.75–1.00 (19.1–25.4)	0.84 (21.4)	—	**456D983H05**
250A short	**5010D23G01**	0.50–0.75 (12.7–19.1)	1.09 (27.7)	—	**456D983H06**
250A short	**5010D23G01**	0.25–0.50 (6.4–12.7)	1.03 (26.2)	—	**456D983H07**
250A long	**5010D23G02**	0.75–1.00 (19.1–25.4)	—	3.88 (98.6)	**5010D23H05**
250A long	**5010D23G02**	0.50–0.75 (12.7–19.1)	—	4.13 (104.9)	**5010D23H06**
250A long	**5010D23G02**	0.25–0.50 (6.4–12.7)	—	4.38 (111.3)	**5010D23H07**



K-Frame ①

Stud Ampere Rating	Stud Catalog Number	Panel Thickness A	Tube Length B	C	Standard Tube Catalog Number	Dimensions D	E	F
400 A short	**6642C14G02**	0.75–1 (19.1–25.4)	0.84 (21.3)	—	**313C909H17**	—	3.66 (93.0)	0.75–16 (19.1–406.4)
400 A short	**6642C14G04**	0.50–0.75 (12.7–18.4)	1.09 (27.69)	—	**313C909H18**	—	—	—
400 A short	**6642C14G06**	0.25–0.5 (6.35–12.7)	1.03 (26.16)	—	**313C909H19**	—	—	—
400 A long	**6642C14G03**	0.75–1 (19.1–25.4)	—	3.78 (96.0)	**313C909H20**	—	—	—
400 A long	**6642C14G05**	0.50–0.75 (12.7–18.4)	—	4.03 (102.4)	**313C909H21**	6.58 (167.1)	—	—
400 A long	**6642C14G07**	0.25 –0.5 (6.35–12.7)	—	4.28 (108.7)	**313C909H22**	—	—	—



Note

① Not UL listed.

Approximate Dimensions in Inches (mm)

L-Frame

Stud Length (A)	Stud Catalog Number
5.47 (138.9)	**314C960G07**
7.97 (202.4)	**314C960G08**
10.47 (265.9)	**314C960G09**



M-Frame

Stud Ampere Rating	Diameter and Thread	Extension Back of Breaker	Stud Catalog Number
225	0.50 (12.7)–13	3.66 (93.0)	**314C960G01**
400	0.75 (19.1)–16	5.91 (150.1)	**314C960G04**
400	0.75 (19.1)–16	8.41 (213.6)	**314C960G05**
400	0.75 (19.1)–16	10.91 (277.0)	**314C960G06**
600	1.00 (25.4)–12	5.91 (150.1)	**314C960G07**
600	1.00 (25.4)–12	8.41 (213.6)	**314C960G08**
600	1.00 (25.4)–12	10.91 (277.0)	**314C960G09**
800	1.13 (28.7)–12	5.91 (150.1)	**314C960G10**
800	1.13 (28.7)–12	8.41 (213.6)	**314C960G11**
800	1.13 (28.7)–12	10.91 (277.0)	**314C960G12**

N-Frame

Stud Ampere Rating	Diameter and Thread	Extension Back of Breaker	Stud Catalog Number
800	1.13 (28.7)–12	5.5 (139.7)	**623B222G01**
800	1.13 (28.7)–12	8.0 (203.2)	**623B222G02**
800	1.13 (28.7)–12	10.5 (266.7)	**623B222G03**
1200	1.25 (31.8)–12	5.5 (139.7)	**373B375G04**
1200	1.25 (31.8)–12	10.5 (266.7)	**373B375G03**

GP, FP, KP, LP and MP Frames

Definite Purpose Molded Case Circuit Breaker Family

Contents

Description	*Page*
Product Selection Guide	**V4-T2-334**
Electrical Characteristics	**V4-T2-334**
Features	**V4-T2-336**
Base Mounting Hardware	**V4-T2-336**
Line and Load Termination	**V4-T2-336**
Optional Line and Load Terminals	**V4-T2-336**
Catalog Number Selection	**V4-T2-337**
Product Selection	**V4-T2-338**
Accessories	**V4-T2-336**
Dimensions	**V4-T2-339**

Learn Online Drawings Online

Definite Purpose Molded Case Circuit Breakers

Optimized solution for HVAC/R and Pumping Applications.

Product Overview

GP, FP, KP, LP and MP Frames 15–800 Amperes NEMA 480 Vac

Eaton's Definite Purpose molded case circuit breakers are available in three-pole configurations, and are designed to meet the specific requirements of HVAC/R and pumping applications.

As with other members of Eaton's family of molded case circuit breakers, Definite Purpose breakers provide high quality, reliability, unmatched performance and outstanding value.

Eaton's Definite Purpose breakers are rated from 15–800 A and are available in five frame sizes. Each frame size has the same compact outside dimensions as Series C breakers.

Additionally, Definite Purpose breakers have been rigorously tested to the UL 489 standard. They are assembled in an ISO certified facility.

Trip Units and Terminals

Definite Purpose breakers contain factory-sealed thermal-magnetic trip units.

The GP-Frame breaker (15–100 A) includes line and load terminals and breaker mounting hardware.

FP (15–225A), KP (200–400 A), LP (450–600 A) and MP (700–800 A) Frames ship standard without mounting hardware. For line and load terminals, add "L" to the end of the catalog number or "W" for no terminals.

External Accessories

Definite Purpose breakers use the same external accessories as Series C breakers: handle mechanisms, motor operators, lock-off devices, busbar extensions and multiple terminal arrangements.

Product Selection Guide

2

Electrical Characteristics

Breaker Type		GPS	FPS	FPH	KPS	KPH
Amperage range		15–100 A	15–225A	15–225A	200–400 A	200–400 A
Performance level		**S**	**S**	**H**	**S**	**H**
Breaker capacity (kA rms)	240 Vac	65	65	100	65	100
NEMA, UL, CSA	480 Vac	22	35	65	35	65
	600 Vac	—	18	25	25	35
Number of poles		3	3	3	3	3
Maximum voltage (Vac)		480	600	600	600	600
Thermal-magnetic		■	■	■	■	■

Electrical Characteristics, continued

Breaker Type		LPS	LPH	MPS	MPH
Amperage range		450–600 A	450–600 A	700–800 A	700–800 A
Performance level		**S**	**H**	**S**	**H**
Breaker capacity (kA rms)	240 Vac	65	100	65	100
NEMA, UL, CSA	480 Vac	35	65	50	65
	600 Vac	25	35	25	35
Number of poles		3	3	3	3
Maximum voltage (Vac)		600	600	600	600
Thermal-magnetic		■	■	■	■

Features

Base Mounting Hardware

English base mounting hardware is included with GP frame only. For all other frames, order base mounting hardware separately as per the table to the right.

Base Mounting Hardware

Frame	Catalog Number English	Metric
GP	Included	—
FP	**BMH1**	**BMH1M**
KP	**BMH3**	**BMH3M**
LP	**BMH4**	**BMH4M**
MP	**BMH5**	**BMH5M**

Note: Base mounting hardware, is included with GP-Frame breakers. A separate catalog number is not required.

Line and Load Terminals

Both line and load terminals are included with GP-Frame Definite Purpose breakers. For all other frames, add "L" for line and load terminals to be included or "W" for no terminals.

Line and Load Termination

Breaker	Termination Type	Awg Wire Range	Metric Wire Range (mm)	Wire Type	Bolt Size English	Bolt Size Metric	Torque Lb–In	Torque Nm	Catalog Number
GP	Wire	#14–1/0	2.5–50	Cu only	—	—	45	5.1	**Included**

Optional Line and Load Terminals

Breaker	Maximum Amperes	Awg Wire Range	Wire Type	Catalog Number	Catalog Number with Control Wire Termination
FP	100	#14–#10	Cu/Al	**3T100FB** ①	—
	100	#8	Cu/Al	**3T100FB** ①	—
	100	#6–#4	Cu/Al	**3T100FB** ①	—
	100	#3–4/0	Cu/Al	**3T100FB** ①	—
	200	#3–4/0	Cu only	**3T150FB** ①	—
	225	#4–4/0	Cu/Al	**3TA225FB** ①	—
	225	#6–300	Cu/Al	**3TA225FDK3** ①	—
	225	#6–300	Cu/Al	**3TA225FDK** ①②	—
KP	400	250–500 (1)	Cu/Al	**TA350K**	—
	400	3/0–250 (2)	Cu/Al	**3TA400K** ①	**3TA400KCW**
LP	500	250–350 (2)	Cu/Al	**TA602LD**	**TA602LDCW**
	600	400–500 (2)	Cu/Al	**3TA603LDK** ①	**3TA603LDKCW**
MP	800	3/0–400 (3)	Cu/Al	**TA800MA2**	**TA800MA2CWT**
	800	500–750 (2)	Cu/Al	**TA801MA**	**TA801MACWT**

Notes

① Package of three terminals.
② Replacement use only.

Accessories

End Cap Accessory Kit

End caps for line and load conductor termination are optional with each breaker. End caps secure the conductor with a ring-type connector. The kit includes one end cap, three cap screws, three nuts and three lock washers.

End Cap Accessory Kit



Series C Accessories

For internal accessories, see **Page V4-T2-273**.

For external accessories, see **Page V4-T2-306**.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.



Ampere Rating				
GP-Frame	**FP-Frame**	**KP-Frame**	**LP-Frame**	**MP-Frame**
015 = 15A	**015** = 15A	**175** = 175A	**450** = 450 A	**700** = 700 A
020 = 20 A	**020** = 20 A	**200** = 200 A	**500** = 500 A	**800** = 800 A
025 = 25 A	**025** = 25 A	**250** = 250 A	**600** = 600 A	
030 = 30 A	**030** = 30 A	**300** = 300 A		
035 = 35A	**035** = 35A	**400** = 400 A		
040 = 40 A	**040** = 40 A			
045 = 45A	**045** = 45A			
050 = 50 A	**050** = 50 A			
060 = 60 A	**060** = 60 A			
070 = 70 A	**070** = 70 A			
080 = 80 A	**080** = 80 A			
090 = 80 A	**100** = 100 A			
100 = 100 A	**110** = 110 A			
	125 = 125A			
	150 = 150 A			
	175 = 175A			
	200 = 200 A			
	225 = 225A			

Notes

① Not available on GP-Frame.

② When choosing a molded case switch, select the highest amperage rating for the frame and the standard interrupting rating.

Product Selection

Catalog Numbers

When ordering Definite Purpose breakers, use the appropriate catalog numbers given below.

GP 100

GP-Frame/15–100 A

Frame/ Ampere Rating	Three-Pole Catalog Number
GP/15–100 A circuit breakers	**GPS3015**
	GPS3020
	GPS3025
	GPS3030
	GPS3035
	GPS3040
	GPS3045
	GPS3050
	GPS3060
	GPS3070
	GPS3080
	GPS3090
	GPS3100
GP/100 A molded case switch	**GPS3100K**

Note: All GP frames come standard with line and load terminals and base mounting hardware. Not available without terminals.

FP 225

FP-Frame/15–225 A

Frame/ Ampere Rating	Three-Pole Catalog Number
FP/15–225A circuit breakers	**FPS3015**
	FPS3020
	FPS3025
	FPS3030
	FPS3035
	FPS3040
	FPS3045
	FPS3050
	FPS3060
	FPS3070
	FPS3080
	FPS3090
	FPS3100
	FPS3110
	FPS3125
	FPS3150
	FPS3175
	FPS3200
	FPS3225
	FPH3015
	FPH3020
	FPH3025
	FPH3030
	FPH3035
	FPH3040
	FPH3045
	FPH3050
	FPH3060
	FPH3070
	FPH3080
	FPH3090
	FPH3100
	FPH3110
	FPH3125
	FPH3150
	FPH3175
	FPH3200
	FPH3225
FP/225A molded case switch	**FPS3225K**

Note: At the end of catalog number, add "L" for terminals or "W" for no terminals.

KP 250

KP-Frame/200–400 A

Frame/ Ampere Rating	Three-Pole Catalog Number
KP/175–400 A circuit breakers	**KPS3175**
	KPS3200
	KPS3250
	KPS3300
	KPS3400
	KPH3175
	KPH3200
	KPH3250
	KPH3300
	KPH3400
KP/400 A molded case switch	**KPS3400K**

LP 400

LP-Frame/450–600 A

Frame/ Ampere Rating	Three-Pole Catalog Number
LP/450–600 A circuit breakers	**LPS3450**
	LPS3500
	LPS3600
	LPH3450
	LPH3500
	LPH3600
LP/600 A molded case switch	**LPS3600K**

MP 800

MP-Frame/700–800 A

Frame/ Ampere Rating	Three-Pole Catalog Number
MP/700–800 A circuit breakers	**MPS3700**
	MPS3800
	MPH3700
	MPH3800
MP/800 A molded case switch	**MPS3800K**

Note: For KP, LP, MP frames above, add "L" for terminals or W" for no terminals to end of catalog number.

Dimensions

Approximate Dimensions in Inches (mm)

All dimensions are provided for guidance and should not be used for construction purposes unless approved.

Contact Eaton for detailed outline drawings.

GP, FP, KP, LP and MP Definite Purpose Frames

	Breaker Type GP	FP	KP	LP	MP
Width	3.00 (76.2)	4.13 (104.9)	5.49 (139.4)	8.25 (209.6)	8.25 (209.6)
Height	4.88 (124.0)	6.00 (152.4)	10.12 (257.0)	10.75 (273.1)	16.00 (406.4)
Depth	2.63 (66.7)	3.38 (85.9)	4.31 (109.6)	3.81 (96.8)	4.06 (103.1)

PM3 Modules

Power Monitoring and Metering with Modbus RTU

Contents

Description	*Page*
PM3 Monitoring and Metering Module	
Product Selection	**V4-T2-341**
Technical Data and Specifications	**V4-T2-341**
Dimensions and Weights	**V4-T2-342**

Learn Online Drawings Online

PM3 Monitoring and Metering Module

Product Description

The PM3 is the perfect solution for main, branch circuit and standalone monitoring/metering applications. With information at your fingertips, you can meter, monitor and communicate phase current and voltage with calculated power and energy.

The PM3 is versatile, as it connects to the load side of a molded-case circuit breaker (MCCB) and communicates easily to a local network or the Internet through Eaton Power Xpert® Gateways (PXGs). Cost of ownership is reduced through ease of installation. The PM3 is your ideal MCCB metering solution.

Application Description

- Communications via Modbus® and Eaton's INCOM™ protocol; compatible with Eaton's PXG for Web page and Ethernet capabilities
- Works in 240 Vac PM3, 480 Vac and 600 Vac applications
  - 480 Vac PM3 has internal power supply to power electronics
  - 600 Vac PM3 requires 24 Vdc auxiliary power
- Seamlessly integrates with thermal-magnetic or electronic trip units

Features and Benefits

- Communicates electrical system data and circuit breaker status
- Calculates power and energy to an accuracy of 1.0% of reading
- Configurable with thermal-magnetic or electronic trip units
- Suitable for reverse-feed applications
- Easy to install

PM3 Benefits When Combined with 310+ Electronic Trip Unit

- Alarming: high load and ground fault
- Zone selective interlocking
- Arcflash Reduction Maintenance System™
- Cause-of-trip localized information through Digiview and TRIP-LED
- Modbus/INCOM communications
- HMI connectivity through PXG
- Current and voltage metering to 0.5% of reading
- Power and energy monitoring to 1.0% of reading
- Reduces cost of ownership

Standards and Certifications

- Meets ANSI C12.1 revenue grade standard with a current and voltage accuracy of 0.5% of reading
- UL 489, Annex J
- IEC 61000-4-2—ESD
- IEC 61000-4-4—EFT
- IEC 61000-4-5—SURGE
- IEC 61000-4-6—EMC
- ANSI C12.1 (1% accuracy)
- UL/cUL/CE

UL Listed c UL us Listed CE

Product Selection

PM3 Modules

Frame	Catalog Number 480 V	600 V
Modbus		
FD	—	**PM3FM**
JG	—	**PM3JM**
KD and LG	—	**PM3LM**
INCOM		
FD	**PM3FI480**	**PM3FI600**
JG	**PM3JI480**	**PM3JI600**
KD and LG	**PM3LI480**	**PM3LI600**

End Cap Kits (Sold Separately)

Frame	Description	Catalog Number
FD	Metric end cap kit for F-Frame	**KPEKM1**
	English end cap kit for F-Frame	**KPEK1**
JG	Metric end cap kit for JG-Frame	**FJ3RTWK**
	English end cap kit for JG-Frame	**FJ3RTDK**
KD	Metric end cap kit for K-Frame	**KPEKM3**
	English end cap kit for K-Frame	**KPEK3**
LG	Metric end cap kit for LG-Frame	**L3RTWK**

Technical Data and Specifications

Metered parameters

- I_A, I_B, I_C
- V_{AB}, V_{BC}, V_{CA}, V_{an}, V_{bn}, V_{cn}
- Apparent Energy, Forward Real Energy, Reverse Real Energy, Net Real Energy, Lagging Reactive Energy, Leading Reactive Energy, Net Reactive Energy
- Apparent Power A, B, C; Apparent Power Total; Reactive Power A, B, C; Reactive Power Total; Real Power A, B, C; Real Power Total
- Frequency, Apparent Power Factor, Apparent PFA, Apparent PFB, Apparent PFC

PM3 Power Monitoring and Communications Module Technical Specifications for Modbus RTU

Description	Specification	
Current Inputs		
Pickup current	0.3A rms	
Maximum reported current	FD/JG 250 A rms	
	KD/LD 630 A rms	
Accuracy	0.5% of reading	
Voltage Inputs		
Range	Line-to-neutral 30–366 Vac	
	Line-to-line 52–635 Vac	
Supported systems	Three-element wye, three-element wye + neutral	
	Two-element delta, four-wire delta systems	
Input impedance	996 kiloohm/phase	
Burden per phase	0.36 VA/phase max. at 600 V; 0.014 VA at 120V	
Phase voltage connections	Internal via screw terminal to busbar For wye system, a neutral is required to be connected to the PM3 on the right Phoenix connector.	
Neutral connection	If neutral is not available, the meter will calculate a virtual neutral based on the phase-to-phase rms voltage. The system voltage must be balanced for this to be accurate.	
Frequency		
Frequency	50/60 Hz	
Accuracy	± 0.1 Hz	
Resolution	0.1 Hz	
Power and Energy		
Accuracy	1% of reading (ANSI C12.1)	
Isolation		
All inputs and outputs are galvanically isolated to 2500 V.		
Environmental Ratings		
Operating temperature	–20 °C to +50 °C	
Storage temperature	–20 °C to +50 °C	
Operating humidity	5 to 95% RH noncondensing	
Sensing Method		
Voltage, current	True rms	
Sampling rate	13.02K samples per second	
Update Rate		
Watts, VAR and VA	1.03 sec at 60 Hz	
All other parameters	1.07 sec at 60 Hz	
Power Supply (External)		
DC voltage	18–30 Vdc	
Maximum current	30.0 mA at 24 Vdc	
Burden	0.72W	
Standard Communication Format		
Connection type	Three-wire RS-485 (A, B, Common)	
Com port baud rate	9600 or 19,200 bauds	Default: 19,200 bauds
Modbus address range	01–247	
Data format	Selectable (8, N, 1 | 8, N, 2 | 8, Even, 1 | 8, Odd, 1)	Default: 8, N, 2
Protocols	Modbus RTU	
Internal termination resistor selectable ON or OFF	Via DIP switch	Default: Enabled

Dimensions and Weights

Approximate Dimensions in Inches (mm)

2

FD Three-Pole with PM3 Modbus



JG Three-Pole with PM3 Modbus



KD Three-Pole with PM3 Modbus



LG Three-Pole with PM3 Modbus



PM3 Dimensions and Shipping Weights

Description	Frame	Dimensions and Weights
Weight in lbs (kg)	FD	1.26 (0.57)
	JG	1.60 (0.73)
	KD/LG	2.25 (1.02)
Basic unit in inches (mm)	FD	4.13 W x 5.00 L x 3.39 H (104.9 x 127.0 x 86.1)
	JG	4.13 W x 5.00 L x 3.39 H (104.9 x 127.0 x 86.1)
	KD/LG	5.48 W x 3.70 L x 4.06 H (139.2 x 94.0 x 103.2)
Shipping container dimensions in inches (mm)	FD/JG	8.00 x 5.13 x 5.50 (203.2 x 130.3 x 139.7)
	KD/LG	6.25 x 8.25 x 7.00 (158.7 x 209.5 x 177.8)

Engine Generator Circuit Breakers

Contents

Description	*Page*
Engine Generator Circuit Breakers	
Catalog Number Selection	**V4-T2-344**
Product Selection	**V4-T2-345**
Accessories Selection Guide and Ordering Information	**V4-T2-347**
Options and Accessories	**V4-T2-347**
Technical Data and Specifications	**V4-T2-348**
Dimensions and Weights	**V4-T2-348**
Direct Current Circuit Breakers	**V4-T2-349**
PVGard Solar Circuit Breakers—600 Vdc Per-Pole and 1000 Vdc Poles-in-Series	**V4-T2-363**
E^2 Mining Service Circuit Breakers	**V4-T2-372**
Classic Mining Breakers	**V4-T2-398**
Add-On Ground Fault Protection—Type GFR	**V4-T2-412**

Learn Online Drawings Online

Engine Generator Circuit Breakers

Product Description

Eaton's engine generator molded case circuit breakers are designed specifically for application on diesel engine powered standby generators where high interrupting circuit breakers are not required. The JG through NG breakers are equipped with a special trip unit, that includes standard thermal (overload) protection and special low magnetic pickup range (FG includes a fixed thermal-magnetic pickup). The standard thermal trip unit provides overload protection for conductors per the National Electrical Code®. The low magnetic pickup range is approximately two to five times the continuous rating and provides closer low-level short-circuit protection when applied on generators that have very low short-circuit capacity. This combination allows the user to customize the breaker to the generator output.

Application Description

Engine generator circuit breakers are suitable for reverse feed application.

Standards and Certifications

Engine generator molded case circuit breakers are designed to conform with the following standards:

- Underwriters Laboratories Standard UL 489, Molded Case Circuit Breakers and Circuit Breaker Enclosures File E7819
- Canadian Standards Association Standard C22.2 No. 5, Service Entrance and Branch Circuit Breakers
- International Electrotechnical Commission Recommendations IEC 947-2, Circuit Breakers

Listed

Conformance with these standards satisfies most local and international codes, assuming user acceptability and simplified application.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers. It is not to be used to build catalog numbers for circuit breakers.

- FG breakers include both line and load side terminals
- JG, KG, LG and NG breakers with **W** catalog number suffix do not include any terminals
- JG, KG, LG and NG breakers without **W** catalog number suffix include both line and load terminals
- Contact Eaton for additional ratings and internal/external accessories
- Reverse feed

Circuit Breakers FG, JG, KG, LG and NG



Product Selection

The following table lists FG through NG engine generator breakers with the maximum generator kVA and kW rating. Engine generator breakers are applied at 115% of the generator full load current rating (FLA). The maximum kW rating is based on three-phase generators at 80% power factor.

Thermal-Magnetic

Magnetic Pickup Range	Maximum Generator Rating 60 Hz 240 Vac kVA ①	kW ②	480 Vac kVA ①	kW ②	600 Vac kVA ①	kW ②	Engine Generator Breaker ③ Catalog Number
Fixed	5	4	11	9	14	11	**FG3015** ④
Fixed	7	6	14	12	18	14	**FG3020** ④
Fixed	9	7	18	14	23	18	**FG3025** ④
Fixed	11	9	22	17	27	22	**FG3030** ④
Fixed	13	10	25	20	32	25	**FG3035** ④
Fixed	14	12	29	23	36	29	**FG3040** ④
Fixed	16	13	32	26	41	32	**FG3045** ④
Fixed	18	14	36	29	45	36	**FG3050** ④
Fixed	22	17	43	35	54	43	**FG3060** ④
Fixed	25	20	51	40	63	51	**FG3070** ④
Fixed	29	23	58	46	72	58	**FG3080** ④
Fixed	32	26	65	52	81	65	**FG3090** ④
Fixed	36	29	72	58	90	72	**FG3100** ④
Fixed	40	32	79	64	99	79	**FG3110** ④
Fixed	45	36	90	72	113	90	**FG3125** ④
Fixed	54	43	108	87	135	108	**FG3150** ④
Fixed	63	51	126	101	158	126	**FG3175** ④
Fixed	72	58	144	116	181	144	**FG3200** ④
Fixed	81	65	162	130	203	162	**FG3225** ④
350–700	63	51	126	101	158	126	**JG3175W** ⑤
350–700	63	51	126	101	158	126	**JG3175** ④
350–700	72	58	144	116	181	144	**JG3200W** ⑤
350–700	72	58	144	116	181	144	**JG3200** ④
350–700	81	65	162	130	203	162	**JG3225W** ⑤
350–700	81	65	162	130	203	162	**JG3225** ④
350–700	90	72	181	144	226	181	**JG3250W** ⑤
350–700	90	72	181	144	226	181	**JG3250** ④
500–1000	108	87	217	173	271	217	**KG3300W** ⑤
500–1000	108	87	217	173	271	217	**KG3300** ④
500–1000	126	101	253	202	316	253	**KG3350W** ⑤
500–1000	126	101	253	202	316	253	**KG3350** ④
1000–2000	144	116	289	231	361	289	**KG3400** ④

Notes

① Breaker continuous current is based on 115% of the generator full load ampere rating.
② Based on three-phase generators at 80% power factor.
③ FG, JG, KG include thermal-magnetic trip units, LG and NG include electronic trip units.
④ Breaker includes line and load terminals.
⑤ Without terminals.

The following catalog numbers have center tap studs for dual voltage applications: JG3070CT, JG3100CT, JG3125CT, KG3175CT, LG3300CTW.

Electronic

Magnetic Pickup Range	Maximum Generator Rating 60 Hz 240 Vac kVA ①	240 Vac kW ②	480 Vac kVA ①	480 Vac kW ②	600 Vac kVA ①	600 Vac kW ②	Engine Generator Breaker ③ Catalog Number
500–2500	162	130	325	260	406	325	**LG3450** ④
500–2500	181	144	361	289	451	361	**LG3500** ④
500–2500	217	173	433	347	542	433	**LG3600** ④
500–2500	253	202	505	404	632	505	**NG3700** ④
500–2500	289	231	578	462	722	578	**NG3800** ④
1250–5000	325	260	650	520	812	650	**NG3900** ④
1250–5000	361	289	722	578	903	722	**NG31000** ④
1250–5000	433	347	867	693	1083	867	**NG31200** ④

Notes

① Breaker continuous current is based on 115% of the generator full load ampere rating.

② Based on three-phase generators at 80% power factor.

③ FG, JG, KG include thermal-magnetic trip units, LG and NG include electronic trip units.

④ Breaker includes line and load terminals.

The following catalog numbers have center tap studs for dual voltage applications: JG3070CT, JG3100CT, JG3125CT, KG3175CT, LG3300CTW.

Accessories Selection Guide and Ordering Information

Enclosures

Type 1 General Purpose

- Surface or flush mounting
- 15–1200 ampere range
- 600 Vac, 500 Vdc

Type 1 enclosed breakers are designed for use in commercial buildings, apartment buildings and other areas where a general purpose enclosure is applicable. The breaker is front operable and is capable of being padlocked in either the ON or OFF position. Ratings through 1200 amperes are listed with Underwriters Laboratories as approved for service entrance application. Both surface and flush mounted enclosures are available.

Type 3R Rainproof Surface Mounting

- Interchangeable hubs (through 400 amperes)
- 15–1200 ampere range
- 600 Vac, 500 Vdc

This general purpose outdoor service center employs a circuit breaker inside a weatherproof sheet steel breaker enclosure to serve as a main disconnect and protective device for feeder circuits. Ratings through 1200 amperes are listed by Underwriters Laboratories as suitable for service entrance application.

Type 12 Dustproof Surface Mounting

- No knockouts or other openings
- 15–1200 ampere range
- 600 Vac, 500 Vdc

The Type 12 enclosure is designed in line with specifications for special industry applications where unusually severe conditions involving oil, coolant, dust and other foreign materials exist in the operating atmosphere. The handle padlocks in the OFF position and the cover is interlocked with the handle mechanism to prevent opening the cover with the circuit breaker in the ON position. Ratings through 1200 amperes are listed by Underwriters Laboratories as suitable for service entrance application.

Enclosure Selection Data

Breaker Frame Amperes	Enclosure Type Class	Catalog Number
FG 15–225	Type 1	**SFDN225**
	Type 3R	**RFDN225**
	Type 12	**JFDN225**
JG 175–250	Type 1	**SJDN250**
	Type 3R	**RJDN250**
	Type 12	**JJDN250**
KG 300–400	Type 1	**SKDN400**
	Type 3R	**RKDN400**
	Type 12	**JKDN400**
LG 450–600	Type 1	**SLDN600**
	Type 3R	**RLDN600**
	Type 12	**JLDN600**
NG 700–1200	Type 1	**SNDN1200**
	Type 3R	**RNDN1200**
	Type 12	**JNDN1200**

Options and Accessories

Standard Terminals

Breaker Frame	Max. Amp Rating	AWG Wire Range	Metric Wire Range mm^2	Catalog Number
FG	100	14–1/0	2.5–50	**3T100FB** ①
FG	150	4–4/0	25–95	**3TA225FD** ①
JG	250	4–350 kcmil	25–185	**TA250KB**
KG	350	250–500 kcmil	120–240	**TA350K**
KG	400	3/0–250 kcmil (2)	95–120	**3TA400K** ①
LG	600	250–500 kcmil (2)	120–240	**3TA603LDK**
NG	700	1–500 kcmil (2)	50–300	**TA700NB1**
NG	1000	3/0–400 kcmil (3)	95–185	**TA1000NB1**
NG	1200	4/0–500 kcmil (4)	120–300	**TA1200NB1**

Neutral Kits, Insulated and Groundable

Max. Enclosure Rating (Amperes)	Main Lug Number Size Cu/Al	Ground Lug Size Cu/Al	Catalog Number
100	(1) 14–1/0	(1) 14–1/0	**INK100**
250	(1) 6–350 kcmil	(1) 4–300 kcmil	**INK250**
400	(1) 4–750 kcmil or (2) 1/0–250 kcmil	(1) 4–300 kcmil	**INK400**
600	(2) 250–500 kcmil	(1) 4–300 kcmil	**INK600**
1200	(3) 1/0 to 750 kcmil or (4) 1/0 to 750 kcmil	(1) 6–250 kcmil	**INK1200**

Internal Accessories

Auxiliary Switch ②

		1A-1B		2A-2B
Breaker Frame	Factory Mounted	Field Kit Catalog Number	Factory Mounted	Field Kit Catalog Number
FG ③	A06	**A1X1PK**	A13	**A2X1RPK**
JG	A06	**A1X2PK**	A13	**A2X2PK**
KG	A06	**A1X3PK**	A13	**A2X3PK**
LG	A06	**A1X4PK**	A13	**A2X4PK**
NG	A06	**A1X5PK**	A13	**A2X5PK**

Shunt Trip ②

Breaker Frame	Rating	Factory Mounted	Field Kit Catalog Number
FG ③	12–24 Vdc	S02	**SNT1LP03K**
JG	12–24 Vdc	S42	**SNT2P04K**
KG	12–24 Vdc	S42	**SNT3P04K**
LG	12–24 Vdc	S02	**SNT4LP03K**
NG	12–24 Vdc	S02	**SNT5LP03K**

Notes

① Package of three terminals.
② Other accessories are available. Same as standard frame breakers.
③ Field installation on the FG Frame is not UL listed.

Technical Data and Specifications

UL 489 Interrupting Capacity Ratings

Volts AC (50/60 Hz)	Interrupting Capacity (Symmetrical Amperes)
240	18,000
480	14,000
600	10,000

IEC 947-2 Interrupting Capacity Ratings

Volts AC (50/60 Hz)	Interrupting Capacity (Symmetrical Amperes)
220, 240	18,000/9,000
380, 415	14,000/7,000
660, 690	18,000/9,000 14,000/7,000 10,000/5,000

Dimensions and Weights

Approximate Dimensions in Inches (mm)

Enclosure Selection Data

Breaker Frame Amperes	Enclosure Type Class	A	B	C	D	E	Approx. Weight Lbs (kg)	Conduit Sizes, Inches	Catalog Number
FG 15–225	Type 1	23.25 (590.6)	8.41 (213.6)	6.28 (159.5)	18.75 (476.3)	1.20 (30.5)	15 (7)	0.25, 0.50, 0.75, 1, 1.25, 1.50, 2, 2.50	**SFDN225**
	Type 3R	25.66 (651.8)	8.84 (224.7)	9.31 (236.5)	24.28 (616.7)	1.70 (43.2)	19 (9)	0.25, 0.50, 0.75, 1, 1.25, 1.50, 2, 2.50	**RFDN225**
	Type 12	25.66 (651.8)	8.84 (224.7)	9.31 (236.5)	24.28 (616.7)	1.70 (43.2)	18 (8)	—	**JFDN225**
JG 175–250	Type 1	34.70 (881.4)	10.92 (277.4)	7.20 (182.9)	30.00 (762.0)	1.88 (47.8)	31 (14)	0.25, 0.50, 2, 2.50, 3	**SJDN250**
	Type 3R	37.50 (952.5)	11.56 (293.6)	10.22 (259.6)	35.77 (908.6)	1.94 (49.3)	40 (18)	0.25, 0.50, 2, 2.50, 3	**RJDN250**
	Type 12	37.53 (953.3)	11.56 (293.6)	10.22 (259.6)	35.77 (908.6)	1.94 (49.3)	37 (17)	—	**JJDN250**
KG 300–400	Type 1	38.81 (985.8)	11.06 (280.9)	10.94 (277.9)	34.00 (863.6)	2.28 (57.9)	53 (24)	0.25, 0.50, 0.75, 1.50, 2, 2.50, 3, 3.50	**SKDN400**
	Type 3R	41.69 (1058.9)	11.75 (298.5)	14.06 (357.1)	39.90 (1013.5)	1.97 (50.0)	60 (27)	0.25, 0.50, 0.75, 2.50, 3, 3.50	**RKDN400**
	Type 12	41.69 (1058.9)	11.75 (298.5)	14.06 (357.1)	39.90 (1013.5)	1.97 (50.0)	53 (24)	—	**JKDN400**
LG 450–600	Type 1	45.88 (1165.4)	14.31 (363.5)	12.38 (314.5)	46.56 (1182.6)	1.91 (48.5)	81 (37)	0.25, 0.50, 0.75, 3, 3.50, 4	**SLDN600**
	Type 3R	48.31 (1227.1)	14.91 (378.7)	15.50 (393.7)	46.56 (1182.6)	1.92 (48.8)	84 (38)	0.25, 0.50, 0.75, 3, 3.50, 4	**RLDN600**
	Type 12	48.31 (1227.1)	14.91 (378.7)	15.50 (393.7)	46.56 (1182.6)	1.92 (48.8)	81 (37)	—	**JLDN600**
NG 700–1200	Type 1	61.22 (1555.0)	21.44 (544.6)	15.41 (391.4)	61.84 (1570.7)	1.97 (50.0)	178 (81)	—	**SNDN1200**
	Type 3R	63.59 (1615.2)	22.00 (558.8)	17.63 (447.8)	61.84 (1570.7)	1.97 (50.0)	175 (79)	—	**RNDN1200**
	Type 12	63.59 (1615.2)	22.00 (558.8)	17.63 (447.8)	61.84 (1570.7)	1.97 (50.0)	170 (77)	—	**JNDN1200**

Type 1 Surface Mounted



Type 3R Rainproof



Type 12, 12K Dustproof



Direct Current Circuit Breakers

Contents

Description	*Page*
Engine Generator Circuit Breakers	**V4-T2-343**
Direct Current Circuit Breakers	
Catalog Number Selection	**V4-T2-351**
Product Selection	**V4-T2-352**
Accessories	**V4-T2-359**
Wiring Diagrams	**V4-T2-361**
Dimensions	**V4-T2-362**
PVGard Solar Circuit Breakers—600 Vdc Per-Pole and 1000 Vdc Poles-in-Series	**V4-T2-363**
E^2 Mining Service Circuit Breakers	**V4-T2-372**
Classic Mining Breakers	**V4-T2-398**
Add-On Ground Fault Protection—Type GFR	**V4-T2-412**

Direct Current Circuit Breakers

Product Description

DC (direct current) systems and applications are becoming commonplace as alternative energy sources have expanded and the number of DC devices and data centers using DC power has swelled.

Eaton offers molded case circuit breakers and switches to meet circuit protection and switching requirements for a host of different DC end user requirements. Applications include UPS battery supply circuits, solar systems and electric vehicle charging, as well as commercial and industrial distribution.

Current ratings are available from 15 to 3000 A, with a full scale of voltage and interrupting ratings to address needs ranging from standard to the highest performance. Optional internal accessories provide remote tripping and indication of breaker status.

The DC breaker family is UL 489 listed and exceeds the requirements in UL 489 Supplement SC for UPS applications. Eaton breakers may be applied in both ungrounded and select grounded applications, with poles connected in series to operate at the maximum voltages shown on **Page V4-T2-350**. To use DC circuit breakers on 600 V grounded systems, three poles in series must be connected on the ungrounded leg.

All DC breakers use the same internal and external accessories as their corresponding Series C and Series G AC frame equivalents, except for the NBDC breaker, which uses the same internal and external accessories as the standard NB frame.

The HFDDC through HMDLDC and EG to RG DC breakers use the same internal and external accessories as their corresponding Series C and Series G AC Frame equivalents. NBDC uses the same internal and external accessories as standard NB breakers.

Many of the Eaton AC molded case circuit breakers carry 250 Vdc ratings for ungrounded systems. Refer to **Pages V4-T2-9** and **V4-T2-118** for these interrupting tables.

Quick Reference Direct Current Circuit Breakers

UL 489 Interrupting Capacity Ratings

Circuit Breaker Type	Maximum Amperes	Interrupting Capacity (kA) Volts DC ① 125	Poles in Series	250 ②	Poles in Series	500	600	Poles in Series	750 ②	Poles in Series
EGEDC	100	10	1	35	2	35	—	3	—	—
EGSDC	100	35	1	42	2	50	—	3	—	—
EGHDC	100	42	1	50	2	65	—	3	—	—
HFDDC	225	42	1	50	2	—	42	3	42	4
JGEDC	250	35	1	35	2	—	35	3	—	—
JGSDC	250	42	1	42	2	—	50	3	—	—
JGHDC	250	50	1	50	2	—	65	3	—	—
HJDDC	250	42	1	50	2	—	42	3	—	—
HKDDC	400	42	1	50	2	—	42	3	—	—
LGEDC	600	22	1	22	2	—	35	3	—	—
LGSDC	600	22	1	22	2	—	50	3	—	—
LGHDC	600	50	1	50	2	—	65	3	—	—
HLDDC	600	42	1	50	2	—	35	3	—	—
HLDDC ③	1200	42	1	50	2	—	—	—	—	—
HMDLDC	800	42	1	50	2	—	35	3	—	—
NBDC	1200	42	1	50	2	—	50	3	—	—
RGHDC	3000	42	1	50	2	—	65	3	—	—

IEC 60947-2 Interrupting Capacity Ratings

Circuit Breaker Type	Maximum Amperes	125 Volts DC Icu	Ics	Poles in Series	250 Volts DC Icu	Ics	Poles in Series	600 Volts DC Icu	Ics	Poles in Series
EGEDC	100	10	10	1	10	10	2	—	—	—
EGSDC	100	35	35	1	35	35	2	—	—	—
EGHDC	100	42	42	1	42	42	2	—	—	—
JGEDC	250	22	22	1	22	22	2	—	—	—
JGSDC	250	22	22	1	22	22	2	—	—	—
JGHDC	250	42	42	1	42	42	2	—	—	—
HJDDC	250	—	—	—	—	—	—	20	10	3
LGEDC	600	22	22	1	22	22	2	—	—	—
LGSDC	600	22	22	1	22	22	2	—	—	—
LGHDC	600	42	42	1	42	42	2	—	—	—
HLDDC	600	—	—	—	—	—	—	20	10	3
HMDLDC	800	—	—	—	—	—	—	20	10	3

Notes

① DC ratings apply to substantially non-inductive circuits. Time constants per UL 489.

② EGEDC through HMDLDC have been tested up to 300 Vdc to allow for battery charging voltages. 750 Vdc is common in transportation applications. HFDDC, four-pole 750 Vdc is available up to 150 A maximum. 300 Vdc and 750 Vdc are not UL 489 listed voltage ratings.

③ Four-pole frame with two-poles connected in parallel.

See **Page V4-T2-361** for series connection diagrams. Use NEC rated cable to connect/short poles in series as shown.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

DC Circuit Breaker

HFDDC 3 150 W

Frame	
EGEDC	= Series G—E (100 A max.)
EGSDC	= Series G—E (100 A max.)
EGHDC	= Series G—E (100 A max.)
HFDDC	= Series C—F (225 A max.)
JGEDC	= Series G—J (250 A max.)
JGSDC	= Series G—J (250 A max.)
JGHDC	= Series G—J (250 A max.)
HJDDC	= Series C—J (250 A max.)
HKDDC	= Series C—K (400 A max.)
LGEDC	= Series G—L (600 A max.)
LGSDC	= Series G—L (600 A max.)
LGHDC	= Series G—L (600 A max.)
HLDDC	= Series C—L (1200 A max.)
HMDLDC	= Series C—M (800 A max.)
NBDC	= NB (1200 A max.)
RGHDC	= Series G—R (3000 A max.)

Number of Poles	
1	= Single-pole
2	= Two-pole
3	= Three-pole
4	= Four-pole

Trip Unit Ampere Rating	
015	= 15 A
020	= 20 A
025	= 25 A
030	= 30 A
035	= 35 A
040	= 40 A
045	= 45 A
050	= 50 A
060	= 60 A
070	= 70 A
080	= 80 A
090	= 90 A
100	= 100 A
110	= 110 A
125	= 125 A
150	= 150 A
175	= 175 A
200	= 200 A
225	= 225 A
250	= 250 A
300	= 300 A
350	= 350 A
400	= 400 A
450	= 450 A
500	= 500 A
600	= 600 A
700	= 700 A
800	= 800 A
900	= 900 A
1000	= 1000 A
1200	= 1200 A
1600	= 1600 A
2000	= 2000 A
2500	= 2500 A
3000	= 3000 A

Suffix	
Series C, NB Frames	
K	= Molded case switch
L	= Line and load terminals, F-Frame
MW	= 135% magnetic trip unit, without terminals
W	= Without terminals
Series G Frames	
FFG	= Fixed thermal, fixed magnetic trip unit, with terminals
FFW	= Fixed thermal, fixed magnetic trip unit, without terminals
FAG	= Fixed thermal, adjustable magnetic trip unit, with terminals
FAW	= Fixed thermal, adjustable magnetic trip unit, without terminals
KSG	= Molded case switch, with terminals
KSW	= Molded case switch, without terminals

Product Selection

Type EGEDC DC Circuit Breakers— Three-Pole High Interrupting Capacity 35 kAIC at 500 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker with Terminals Catalog Number	Complete Circuit Breaker without Terminals Catalog Number
25	EGEDC3025FFG	EGEDC3025FFW
30	EGEDC3030FFG	EGEDC3030FFW
35	EGEDC3035FFG	EGEDC3035FFW
40	EGEDC3040FFG	EGEDC3040FFW
45	EGEDC3045FFG	EGEDC3045FFW
50	EGEDC3050FFG	EGEDC3050FFW
60	EGEDC3060FFG	EGEDC3060FFW
70	EGEDC3070FFG	EGEDC3070FFW
80	EGEDC3080FFG	EGEDC3080FFW
90	EGEDC3090FFG	EGEDC3090FFW
100	EGEDC3100FFG	EGEDC3100FFW

Type EGSDC DC Circuit Breakers— Three-Pole High Interrupting Capacity 50 kAIC at 500 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker with Terminals Catalog Number	Complete Circuit Breaker without Terminals Catalog Number
25	EGSDC3025FFG	EGSDC3025FFW
30	EGSDC3030FFG	EGSDC3030FFW
35	EGSDC3035FFG	EGSDC3035FFW
40	EGSDC3040FFG	EGSDC3040FFW
45	EGSDC3045FFG	EGSDC3045FFW
50	EGSDC3050FFG	EGSDC3050FFW
60	EGSDC3060FFG	EGSDC3060FFW
70	EGSDC3070FFG	EGSDC3070FFW
80	EGSDC3080FFG	EGSDC3080FFW
90	EGSDC3090FFG	EGSDC3090FFW
100	EGSDC3100FFG	EGSDC3100FFW

Type EGHDC DC Circuit Breakers— Three-Pole High Interrupting Capacity 65 kAIC at 500 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker with Terminals Catalog Number	Complete Circuit Breaker without Terminals Catalog Number
25	EGHDC3025FFG	EGHDC3025FFW
30	EGHDC3030FFG	EGHDC3030FFW
35	EGHDC3035FFG	EGHDC3035FFW
40	EGHDC3040FFG	EGHDC3040FFW
45	EGHDC3045FFG	EGHDC3045FFW
50	EGHDC3050FFG	EGHDC3050FFW
60	EGHDC3060FFG	EGHDC3060FFW
70	EGHDC3070FFG	EGHDC3070FFW
80	EGHDC3080FFG	EGHDC3080FFW
90	EGHDC3090FFG	EGHDC3090FFW
100	EGHDC3100FFG	EGHDC3100FFW

HFDDC

Type HFDDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 42 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker with Line and Load Terminals ① Single-Pole Catalog Number	Two-Pole Catalog Number	Three-Pole Catalog Number	Four-Pole Catalog Number
15	HFDDC1015L	HFDDC2015L	HFDDC3015L	HFDDC4015L
20	HFDDC1020L	HFDDC2020L	HFDDC3020L	HFDDC4020L
25	HFDDC1025L	HFDDC2025L	HFDDC3025L	HFDDC4025L
30	HFDDC1030L	HFDDC2030L	HFDDC3030L	HFDDC4030L
35	HFDDC1035L	HFDDC2035L	HFDDC3035L	HFDDC4035L
40	HFDDC1040L	HFDDC2040L	HFDDC3040L	HFDDC4040L
45	HFDDC1045L	HFDDC2045L	HFDDC3045L	HFDDC4045L
50	HFDDC1050L	HFDDC2050L	HFDDC3050L	HFDDC4050L
60	HFDDC1060L	HFDDC2060L	HFDDC3060L	HFDDC4060L
70	HFDDC1070L	HFDDC2070L	HFDDC3070L	HFDDC4070L
80	HFDDC1080L	HFDDC2080L	HFDDC3080L	HFDDC4080L
90	HFDDC1090L	HFDDC2090L	HFDDC3090L	HFDDC4090L
100	HFDDC1100L	HFDDC2100L	HFDDC3100L	HFDDC4100L
110	HFDDC1110L	HFDDC2110L	HFDDC3110L	HFDDC4110L
125	HFDDC1125L	HFDDC2125L	HFDDC3125L	HFDDC4125L
150	HFDDC1150L	HFDDC2150L	HFDDC3150L	HFDDC4150L
175	—	HFDDC2175L	HFDDC3175L	—
200	—	HFDDC2200L	HFDDC3200L	—
225	—	HFDDC2225L	HFDDC3225L	—

Type JGEDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 35 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ② Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
70	JGEDC3070FAG	JGEDC3250NN	JT3070FA	T250FJ
90	JGEDC3090FAG	JGEDC3250NN	JT3090FA	T250FJ
100	JGEDC3100FAG	JGEDC3250NN	JT3100FA	T250FJ
125	JGEDC3125FAG	JGEDC3250NN	JT3125FA	T250FJ
150	JGEDC3150FAG	JGEDC3250NN	JT3150FA	T250FJ
175	JGEDC3175FAG	JGEDC3250NN	JT3175FA	T250FJ
200	JGEDC3200FAG	JGEDC3250NN	JT3200FA	T250FJ
225	JGEDC3225FAG	JGEDC3250NN	JT3225FA	T250FJ
250	JGEDC3250FAG	JGEDC3250NN	JT3250FA	T250FJ

Notes

① For breaker without terminals, replace "L" with "W" at end of catalog number.

② For complete breaker, order individual frame, trip unit and terminals for field installation.

Type JGSDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 50 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
70	JGSDC3070FAG	JGSDC3250NN	JT3070FA	T250FJ
90	JGSDC3090FAG	JGSDC3250NN	JT3090FA	T250FJ
100	JGSDC3100FAG	JGSDC3250NN	JT3100FA	T250FJ
125	JGSDC3125FAG	JGSDC3250NN	JT3125FA	T250FJ
150	JGSDC3150FAG	JGSDC3250NN	JT3150FA	T250FJ
175	JGSDC3175FAG	JGSDC3250NN	JT3175FA	T250FJ
200	JGSDC3200FAG	JGSDC3250NN	JT3200FA	T250FJ
225	JGSDC3225FAG	JGSDC3250NN	JT3225FA	T250FJ
250	JGSDC3250FAG	JGSDC3250NN	JT3250FA	T250FJ

JGHDC3250NN

Type JGHDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 65 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
70	JGHDC3070FAG	JGHDC3250NN	JT3070FA	T250FJ
90	JGHDC3090FAG	JGHDC3250NN	JT3090FA	T250FJ
100	JGHDC3100FAG	JGHDC3250NN	JT3100FA	T250FJ
125	JGHDC3125FAG	JGHDC3250NN	JT3125FA	T250FJ
150	JGHDC3150FAG	JGHDC3250NN	JT3150FA	T250FJ
175	JGHDC3175FAG	JGHDC3250NN	JT3175FA	T250FJ
200	JGHDC3200FAG	JGHDC3250NN	JT3200FA	T250FJ
225	JGHDC3225FAG	JGHDC3250NN	JT3225FA	T250FJ
250	JGHDC3250FAG	JGHDC3250NN	JT3250FA	T250FJ

HJDDC3250

Type HJDDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 42 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
70	HJDDC3250F	JT3070T	TA250KB
90	HJDDC3250F	JT3090T	TA250KB
100	HJDDC3250F	JT3100T	TA250KB
125	HJDDC3250F	JT3125T	TA250KB
150	HJDDC3250F	JT3150T	TA250KB
175	HJDDC3250F	JT3175T	TA250KB
200	HJDDC3250F	JT3200T	TA250KB
225	HJDDC3250F	JT3225T	TA250KB
250	HJDDC3250F	JT3250T	TA250KB

Note

① For complete breaker, order individual frame, trip unit and terminals for field installation.

HKDDC3400

Type HKDDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 42 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
100	HKDDC3400F	KT3100T	TA300K
125	HKDDC3400F	KT3125T	TA300K
150	HKDDC3400F	KT3150T	TA300K
175	HKDDC3400F	KT3175T	TA300K
200	HKDDC3400F	KT3200T	TA300K
225	HKDDC3400F	KT3225T	TA300K
250	HKDDC3400F	KT3250T	TA350K
300	HKDDC3400F	KT3300T	TA350K
350	HKDDC3400F	KT3350T	TA350K
400	HKDDC3400F	KT3400T	3TA400K ②

LGEDC3630NN

Type LGEDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 35 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
250	LGEDC3250FAG	LGEDC3630NN	LT3250FA	TA350LK
300	LGEDC3300FAG	LGEDC3630NN	LT3300FA	TA350LK
350	LGEDC3350FAG	LGEDC3630NN	LT3350FA	TA350LK
400	LGEDC3400FAG	LGEDC3630NN	LT3400FA	TA350LK
500	LGEDC3500FAG	LGEDC3630NN	LT4500FA	3TA632LK ②
600	LGEDC3600FAG	LGEDC3630NN	LT3600FA	3TA632LK ②

Type LGSDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 50 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
250	LGSDC3250FAG	LGSDC3630NN	LT3250FA	TA350LK
300	LGSDC3300FAG	LGSDC3630NN	LT3300FA	TA350LK
350	LGSDC3350FAG	LGSDC3630NN	LT3350FA	TA350LK
400	LGSDC3400FAG	LGSDC3630NN	LT3400FA	TA350LK
500	LGSDC3500FAG	LGSDC3630NN	LT4500FA	3TA632LK ②
600	LGSDC3600FAG	LGSDC3630NN	LT3600FA	3TA632LK ②

Notes

① For complete breaker, order individual frame, trip unit and terminals for field installation.

② Three-pole kit.

Type LGHDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 65 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
250	**LGHDC3250FAG**	**LGHDC3630NN**	**LT3250FA**	**TA350LK**
300	**LGHDC3300FAG**	**LGHDC3630NN**	**LT3300FA**	**TA350LK**
350	**LGHDC3350FAG**	**LGHDC3630NN**	**LT3350FA**	**TA350LK**
400	**LGHDC3400FAG**	**LGHDC3630NN**	**LT3400FA**	**TA350LK**
500	**LGHDC3500FAG**	**LGHDC3630NN**	**LT4500FA**	**3TA632LK** ②
600	**LGHDC3600FAG**	**LGHDC3630NN**	**LT3600FA**	**3TA632LK** ②

HLDDC

Type HLDDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 35 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
300	**HLDDC3600F**	**LT3300T**	**TA602LD**
350	**HLDDC3600F**	**LT3350T**	**TA602LD**
400	**HLDDC3600F**	**LT3400T**	**TA602LD**
450	**HLDDC3600F**	**LT3450T**	**TA602LD**
500	**HLDDC3600F**	**LT3500T**	**TA602LD**
600	**HLDDC3600F**	**LT3600T**	**3TA603LDK** ②

Type HLDDC DC Circuit Breakers—Two-Pole High Interrupting Capacity 50 kAIC at 250 Vdc ③④

Maximum Continuous Ampere Rating at 40 °C	Complete Breaker Catalog Number
600	**HLDDC20600**
700	**HLDDC20700**
800	**HLDDC20800**
900	**HLDDC20900**
1000	**HLDDC21000**
1200	**HLDDC21200**

Notes

① For complete breaker, order individual frame, trip unit and terminals for field installation.

② Three-pole kit.

③ Includes breaker frame, trip unit and terminals.

④ Four-pole breaker with two poles wired in parallel.

HMDLDC3800F

Type HMDLDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 35 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Circuit Breaker Frame Only ① Catalog Number	Thermal-Magnetic Trip Unit Catalog Number	Standard Terminals Catalog Number
300	**HMDLDC3800F**	**MT3300T**	**TA700MA1**
350	**HMDLDC3800F**	**MT3350T**	**TA700MA1**
400	**HMDLDC3800F**	**MT3400T**	**TA700MA1**
450	**HMDLDC3800F**	**MT3450T**	**TA700MA1**
500	**HMDLDC3800F**	**MT3500T**	**TA700MA1**
600	**HMDLDC3800F**	**MT3600T**	**TA700MA1**
700	**HMDLDC3800F**	**MT3700T**	**TA700MA1**
800	**HMDLDC3800F**	**MT3800T**	**TA800MA2**

Type NBDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 50 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker Factory Assembled without Terminals ② Catalog Number	Includes Magnetic Trip Unit Calibrated at 135%	Standard Terminals Catalog Number
700	**NBDC3700MW**	Included	**TA1000NB1**
800	**NBDC3800MW**	Included	**TA1000NB1**
900	**NBDC3900MW**	Included	**TA1000NB1**
1000	**NBDC31000MW**	Included	**TA1000NB1**
1200	**NBDC31200MW**	Included	**TA1200NB1**

RGHDC3300FFWM

Type RGHDC DC Circuit Breakers—Three-Pole High Interrupting Capacity 65 kAIC at 600 Vdc

Maximum Continuous Ampere Rating at 40 °C	Complete Circuit Breaker Factory Assembled ② Imperial Mounting Hardware Catalog Number	Metric Mounting Hardware Catalog Number	Includes Magnetic Trip Unit Calibrated at 135%	Standard Rear Connectors Catalog Number
1600	**RGHDC3160FFWE**	**RGHDC3160FFWM**	Included	**B2016RDM**
2000	**RGHDC3200FFWE**	**RGHDC3200FFWM**	Included	**B2016RDM**
2500	**RGHDC3250FFWE**	**RGHDC3250FFWM**	Included	**B2500RDM**
3000	**RGHDC3300FFWE**	**RGHDC3300FFWM**	Included	**B3000RDM**

Notes

① Includes frame and trip unit. Order terminals or connectors separately.

② Six rear connectors included as standard complete circuit breaker.

DC Breaker Terminal Wire Ranges

Breaker Frame	Maximum Breaker Ampacity	Terminal Body Material	Wire Type	AWG Wire Range/ Number of Conductors	Metric Wire Range mm^2	Number of Terminals Included	Standard Terminal Catalog Number
EGEDC, EGSDC, EGHDC	100	Aluminum	Cu/Al	14–1/0	2.5–50	3	**3TA125EF**
HFDDC	20	Steel	Cu/Al	14–10 (1)	2.5–4 (1)	3	**3T20FB**
	100	Steel	Cu/Al	14–1/0 (1)	2.5–50 (1)	3	**3T100FB**
	225	Aluminum	Cu/Al	4–4/0 (1)	25–95 (1)	3	**3TA225FD**
JGEDC, JGSDC, JGHDC	250	Stainless steel	Cu	4–350 (1)	25–185 (1)	1	**T250FJ**
HJDDC	250	Aluminum	Cu/Al	4–350 kcmil (1)	25–185 (1)	1	**TA250KB**
HKDDC	225	Aluminum	Cu/Al	3–350 kcmil (1)	35–185 (1)	1	**TA300K**
	350	Aluminum	Cu/Al	250–500 kcmil (1)	120–240 (1)	1	**TA350K**
	400	Aluminum	Cu/Al	3/0–250 kcmil (2)	95–120 (1)	3	**3TA400K**
LGEDC, LGSDC, LGHDC	400	Aluminum	Cu/Al	2–500 (1)	35–240 (1)	1	**TA350LK**
	630	Aluminum	Cu/Al	2–500 kcmil (2)	35–240 (2)	1	**TA632L**
	630	Aluminum	Cu/Al	2–500 kcmil (2)	35–240 (2)	3	**3TA632LK**
HLDDC	500	Aluminum	Cu/Al	3/0–350 kcmil (2)	95–150 (2)	1	**TA602LD**
	600	Aluminum	Cu/Al	400–500 kcmil (2)	185–240 (2)	3	**3TA603LDK**
HMDLDC	600	Aluminum	Cu/Al	1–500 kcmil (2)	—	1	**TA700MA1**
	800	Aluminum	Cu/Al	3/0–400 kcmil (3)	—	1	**TA800MA2**
NBDC	700	Aluminum	Cu/Al	3/0–400 kcmil (3)	95–185 (3)	1	**TA1000NB1**
	800	Aluminum	Cu/Al	3/0–400 kcmil (3)	95–185 (3)	1	**TA1000NB1**
	900	Aluminum	Cu/Al	3/0–400 kcmil (3)	95–185 (3)	1	**TA1000NB1**
	1000	Aluminum	Cu/Al	3/0–400 kcmil (3)	95–185 (3)	1	**TA1000NB1**
	1200	Aluminum	Cu/Al	4/0–500 kcmil (4)	120–240 (4)	1	**TA1200NB1**

Note: RGHDC breakers include six rear connectors as standard.

Molded Case Switches

Eaton's DC molded case switches are used in applications requiring a compact, high-capacity disconnect. They are UL 489 listed and have automatic high instantaneous current protection. These devices do not provide overload protection.

Molded Case Switches

Maximum Continuous Ampere Rating at 40 °C	Interrupting Capacity (Volts DC)	Poles in Series	With Line and Load Terminals Catalog Number	Without Line and Load Terminals Catalog Number
600 Vdc Maximum				
100	42	3	**HFDDC3100KL**	**HFDDC3100KW**
150	42	3	**HFDDC3150KL**	**HFDDC3150KW**
225	42	3	**HFDDC3225KL**	**HFDDC3225KW**
250	65	3	**JGKDC3250KSG**	**JGKDC3250KSW**
250	42	3	**HJDDC3250K**	**HJDDC3250KW**
400	35	3	**HKDDC3400K**	**HKDDC3400KW**
	65	3	**LGKDC3400KSG**	**LGKDC3400KSW**
600	65	3	**LGKDC3630KSG**	**LGKDC3630KSW**
	35	3	**HLDDC3600K**	**HLDDC3600WK**
800	35	3	**HMDLDC3800K**	**HMDLDC3800WK**
500 Vdc Maximum				
100	65	3	**EGK3100KSG**	**EGK3100KSW**
250 Vdc Maximum				
100	50	2	**HFDDC2100KL**	**HFDDC2100KW**
150	50	2	**HFDDC2150KL**	**HFDDC2150KW**
225	50	2	**HFDDC2225KL**	**HFDDC2225KW**
1200	50	①	**HLDDC21200K** ①	**HLDDC21200WK** ①

Note

① Four-pole frame with two-pole connected in parallel.

Accessories

Internal Accessories

		Field Installation Kits								
Description	**Factory Installation (HFDDC)**	**HFDDC** ①	**EGEDC, EGSDC, EGHDC**	**JGEDC, JGSDC, JGHDC LGEDC, LGSDC, LGHDC**	**HJDDC**	**HKDDC**	**HLDDC**	**HMDLDC**	**NBDC**	**RGHDC**
Right-Pole Mounting										
Auxiliary switch										
1A-1B	A06	A1X1PK	AUX1A1BPK	AUX1A1BPK	A1X2PK	A1X3PK	A1X4PK	A1X4PK	4980D16G05	—
2A-2B	A13	A2X1RPK	AUX2A2BPK	AUX2A2BPK	A2X2PK	A2X3PK	A2X4PK	A2X4PK	4980D16G06	A2X6RPK
Alarm switch										
1 make/1 break	B06	A1L1RPK	ALM1M1BEPK	ALM1M1BJPK	A1L2RPK	A1L3RPK	A1L4RPK	A1L4RPK	—	A1L6RPK
Auxiliary and alarm combo										
1A-1B, 1 make/1 break	C05	AAL1RPK	AUXALRMEPK	AUXALRMJPK	AAL2RPK	AAL3RPK	AA114RPK	AA114RPK	—	—
Left-Pole Mounting										
Shunt trip										
12 Vdc	S02	SNT1LP03K	SNT012CPK	SNT012CPK	SNT2P04K	SNT3P04K	SNT4LP03K	SNT4LP03K	2606D58G14	—
24 Vdc	S02	SNT1LP03K	SNT024CPK	SNT024CPK	SNT2P04K	SNT3P04K	SNT4LP03K	SNT4LP03K	2606D58G13	SNT6P03K ②
48 Vdc	S06	SNT1LP08K	SNT4860CPK	SNT4860CPK	SNT2P06K	SNT3P06K	SNT4LP23K	SNT4LP23K	2606D58G12	SNT6P23K ②
60 Vdc	S06	SNT1LP08K	SNT4860CPK	SNT4860CPK	SNT2P06K	SNT3P06K	SNT4LP23K	SNT4LP23K	2606D58G11	SNT6P23K ②
125 Vdc	S10	SNT1LP12K	SNT120CPK	SNT120CPK	SNT2P11K	SNT3P11K	SNT4LP26K	SNT4LP26K	2606D58G10	SNT6P23K ②
250 Vdc	S14	SNT1LP18K	—	—	SNT2P14K	SNT3P14K	SNT4LP14K	SNT4LP14K	2606D58G09	SNT6P14K
120 Vac	S06	SNT1LP12K	SNT120CPK	SNT120CPK	SNT2P11K	SNT3P11K	SNT4LP11K	SNT4LP11K	2060D58G05	SNT6P11K ②
Undervoltage release										
12 Vdc	U30	UVH1LP20K	UVR012DPK	UVR012DPK	UVH2LP20K	UVH3LP20K	UVH4LP20K	UVH4LP20K	372D032G06	UVH6RP20K ②
24 Vdc	U34	UVH1LP21K	UVR024DPK	UVR024DPK	UVH2LP21K	UVH3LP21K	UVH4LP21K	UVH4LP21K	372D032G07	UVH6RP21K ②
48 Vdc	U38	UVH1LP22K	UVR048DPK	UVR048DPK	UVH2LP22K	UVH3LP22K	UVH4LP22K	UVH4LP22K	372D032G08	UVH6RP23K ②
125 Vdc	U42	UVH1LP26K	UVR125DPK	UVR125DPK	UVH2LP26K	UVH3LP26K	UVH4LP26K	UVH4LP26K	372D032G09	UVH6RP26K ②
250 Vdc	U46	UVH1LP28K	UVR250DPK	UVR250DPK	UVH2LP28K	UVH3LP28K	UVH4LP28K	UVH4LP28K	372D032G10	UVH6RP28K ②
120 Vac	U14	UVH1LP08K	UVR120APK	UVR120APK	UVH2LP08K	UVH3LP08K	UVH4LP08K	UVH4LP08K	373D632G05	UVH6RP08K ②

Notes

① F-Frame circuit breakers are factory sealed. Underwriters Laboratories requires that internal accessories be installed at the factory. Internal accessories are UL listed for factory installation under E7819. Where local codes and standards permit and UL listing is not required, internal accessories can be field installed. Accessory installation should be done before the circuit breaker is mounted and connected.

② Right-pole mounted.

One accessory can be mounted per pole, per breaker. Factory installation of accessories is available. Contact Eaton for assistance with part number configuration.

2

Jumpers

Jumpers must be ordered separately. Priced individually.

HFDDC Frame

Description	Maximum Amperes	Catalog Number
Single copper jumper	60	**DC1F060** ①
	100	**DC1F100** ①
	125	**DC1F125** ①
	225	**DC1F225** ①

HKDDC Frame

Description	Maximum Amperes	Catalog Number
Single copper jumper	400	**DC1K400** ①

LGEDC, LGSDC, LGHDC Frames

Description	Maximum Amperes	Catalog Number
Package of 2 aluminum jumpers	400	**DC2LG400A**
Package of 3 aluminum jumpers	400	**DC3LG400A**
Package of 30 aluminum jumpers	400	**DC30LG400A**

Note

① Not UL Listed; Non UL listed jumpers used in a UL application may need to be qualified by the OEM in their assembly. This may take place with UL or another certified testing agency.

Wiring Diagrams

Series Connection Diagrams for DC Application ①②

250 Vdc Maximum—Two Poles in Series



Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.



Suitable for use on ungrounded systems only.

500 Vdc or 600 Vdc Maximum—Three Poles in Series



Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.



Suitable for use on ungrounded systems only.

750 Vdc Maximum—Four Poles in Series



Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.



Suitable for use on ungrounded systems only.

Notes

① Poles in series connection is customer supplied. Use rated cable per NEC.

② For grounded systems, all poles in series must be connected on non-grounded terminal, with load connected to grounded terminal.

Dimensions

Approximate Dimensions in Inches (mm)

DC Breaker Dimensions

Frame	Number of Poles	Width	Height	Depth
EGEDC, EGSDC, EGHDC	3	3.00 (76.2)	5.50 (139.7)	2.99 (75.9)
HFDDC	1	1.38 (35.1)	6.00 (152.4)	3.38 (86.0)
	2	2.75 (70.0)	6.00 (152.4)	3.38 (86.0)
	3	4.13 (105.0)	6.00 (152.4)	3.38 (86.0)
	4	5.50 (139.7)	6.00 (152.4)	3.38 (86.0)
JGEDC, JGSDC, JGHDC	3	4.13 (104.9)	7.00 (177.8)	3.57 (90.7)
HJDDC	2, 3	4.13 (105.0)	10.00 (254.0)	4.06 (103.1)
HKDDC	2, 3	5.50 (139.7)	10.13 (257.3)	4.10 (104.1)
LGEDC, LGSDC, LGHDC	3	5.48 (139.2)	10.13 (257.3)	4.09 (103.9)
600 A Max. HLDDC	2, 3	8.25 (209.6)	10.75 (273.1)	4.06 (103.1)
1200 A Max. HLDDC	4	11.00 (279.4)	10.75 (273.1)	4.06 (103.1)
HMDLDC	2, 3	8.25 (209.6)	16.00 (406.4)	4.06 (103.1)
NBDC	3	8.25 (209.6)	16.00 (406.4)	5.50 (139.7)
RGHDC	3	15.50 (393.7)	16.00 (406.4)	9.75 (247.7)

PVGard Solar Photovoltaic Circuit Breakers

Contents

Description	*Page*
Engine Generator Circuit Breakers	**V4-T2-343**
Direct Current Circuit Breakers	**V4-T2-349**
PVGard Solar Circuit Breaker—1000 Vdc Poles-in-Series	
Features	**V4-T2-364**
Standards and Certifications	**V4-T2-364**
Product Selection	**V4-T2-365**
Accessories	**V4-T2-366**
Technical Data and Specifications	**V4-T2-369**
Dimensions	**V4-T2-371**
Wiring Diagrams	**V4-T2-371**
E^2 Mining Service Circuit Breakers	**V4-T2-372**
Classic Mining Breakers	**V4-T2-398**
Add-On Ground Fault Protection—Type GFR	**V4-T2-412**

PVGard Solar Circuit Breaker—1000 Vdc Poles-in-Series

Product Overview

- PVGard lineup
  - 1000 Vdc poles-in-series breaker and switch. Requires poles in series connection
- UL 489B listed for solar photovoltaic circuit protection
- 50 °C calibration
- Offers both 100% and 80% rated breakers
- Handle bi-directional current flow

Product Description

Photovoltaic (PV) systems convert the energy of the sun into electrical power that is fed directly into the electric grid. Within the balance of system (BOS), direct current (DC) circuit breakers protect the wiring connected from the PV modules to the combiner or the inverter, while also behaving as a disconnect.

Eaton is a global leader in circuit protection and brings this expertise to bear in the photovoltaic market. PVGard solar circuit breakers are part of a product family that combines a disconnect with circuit protection in a single, compact, resettable device to protect and isolate DC circuits as needed in photovoltaic systems. PVGard breakers can replace fuses, fuse holders and disconnects in combiner box and inverter applications—saving space, streamlining design, purchasing and receiving, and reducing spare parts requirements.

This 1000 Vdc poles-in-series lineup provides reliable and safe disconnect means and overcurrent protection in a single, compact device for commercial and utility scale PV systems. This solution does not require jumpers with the breaker/switch to be a UL 489B listed device, providing reliability and flexibility in design without limitation on implementation of the breaker/switch. If needed, cost-effective Eaton jumpers can be included.

Application Description

Photovoltaic (PV) systems convert the energy of the sun into electrical power that is fed directly into the electric grid. PVGard circuit breakers are used to protect the wiring from the modules to the combiner box or inverter from overcurrents, and to provide an isolation mechanism.

Features

PVGard breakers are uniquely designed with these features:

- Meets the higher voltage and lower fault current levels of solar systems
- Tested to extreme ambient conditions from –40°C to +90°C
- Full complement of accessories for status, signalling, and on/off operation remotely
- Can handle bi-directional flow of current
- Can be applied in grounded, ungrounded or bi-polar systems
- Meets and exceeds the standards of UL 489B for photovoltaic molded case circuit breakers and molded case switches
- Available both standard (80%-rated) and 100%-rated breakers
- 50°C calibration
- Ability to open on signal from DC arc or ground fault detector
- Wide range of current ratings increases options for matching incoming strings
- Eliminates fuse stocking costs and matching issues

Designed specifically for high- and low-temperature demands of PV installations, PVGard circuit breakers undergo extreme ambient cycling tests, and carry a robust operating temperature range. Trip units calibrate at 100% and 80% of nameplate current in a 50°C ambient, ensuring continuous operation in higher temperature environments typical to solar.

Rigorous third-party testing includes limited and standard fault current tests, electrical and mechanical endurance, di-electric voltage withstand and temperature tests. Eaton's PVGard products are stand-alone devices without requiring jumpers to be UL 489B listed devices.

PVGard breakers are available with a full complement of accessories to provide string status, enable remote trip, on/off operation, and can be customized to site requirements.

Standards and Certifications

- Designed to meet UL 489B for solar photovoltaic circuit protection
- UL File E350638, Category Control Number DIUR

Listed

Product Selection

Catalog number includes breaker frame and trip unit. Order terminals separately. See **Page V4-T2-368**.

FD PV Frame

FD PV Frame, 100 A Maximum, 1000 Vdc, 3 kA ①

Current Rating Amperes	Poles in Series	Trip Unit	80% Rated Catalog Number	100% Rated Catalog Number
30	4	Fixed thermal, fixed magnetic	**FDPV4030W**	**CFDPV4030W**
40	4	Fixed thermal, fixed magnetic	**FDPV4040W**	**CFDPV4040W**
50	4	Fixed thermal, fixed magnetic	**FDPV4050W**	**CFDPV4050W**
60	4	Fixed thermal, fixed magnetic	**FDPV4060W**	**CFDPV4060W**
70	4	Fixed thermal, fixed magnetic	**FDPV4070W**	**CFDPV4070W**
80	4	Fixed thermal, fixed magnetic	**FDPV4080W**	**CFDPV4080W**
90	4	Fixed thermal, fixed magnetic	**FDPV4090W**	**CFDPV4090W**
100	4	Fixed thermal, fixed magnetic	**FDPV4100W**	**CFDPV4100W**

KD PV Frame

KD PV Frame, 350 A Maximum, 1000 Vdc, 5 kA ①

Current Rating Amperes	Poles in Series	Trip Unit	80% Rated Catalog Number	100% Rated Catalog Number
125	4	Fixed thermal, fixed magnetic	**KDPV4125W**	**CKDPV4125W**
150	4	Fixed thermal, fixed magnetic	**KDPV4150W**	**CKDPV4150W**
175	4	Fixed thermal, fixed magnetic	**KDPV4175W**	**CKDPV4175W**
200	4	Fixed thermal, fixed magnetic	**KDPV4200W**	**CKDPV4200W**
225	4	Fixed thermal, fixed magnetic	**KDPV4225W**	**CKDPV4225W**
250	4	Fixed thermal, fixed magnetic	**KDPV4250W**	**CKDPV4250W**
300	4	Fixed thermal, fixed magnetic	**KDPV4300W**	**CKDPV4300W**
350	4	Fixed thermal, fixed magnetic	**KDPV4350W**	**CKDPV4350W**

LG PV Frame

LG PV Frame, 400 A Maximum, 1000 Vdc, 5 kA ①

Current Rating Amperes	Poles in Series	Trip Unit	80% Rated Catalog Number	100% Rated Catalog Number
250	4	Fixed thermal, fixed magnetic	**LGPV4250W**	**CLGPV4250W**
300	4	Fixed thermal, fixed magnetic	**LGPV4300W**	**CLGPV4300W**
350	4	Fixed thermal, fixed magnetic	**LGPV4350W**	**CLGPV4350W**
400	4	Fixed thermal, fixed magnetic	**LGPV4400W**	**CLGPV4400W**

MDL PV Frame

MDL PV Frame, 600 A Maximum, 1000 Vdc, 7.5 kA ①

Current Rating Amperes	Poles in Series	Trip Unit	80% Rated Catalog Number	100% Rated Catalog Number
300	3	Fixed thermal, fixed magnetic	**MDLPV3300W**	**CMDLPV3300W**
350	3	Fixed thermal, fixed magnetic	**MDLPV3350W**	**CMDLPV3350W**
400	3	Fixed thermal, fixed magnetic	**MDLPV3400W**	**CMDLPV3400W**
450	3	Fixed thermal, fixed magnetic	**MDLPV3450W**	**CMDLPV3450W**
500	3	Fixed thermal, fixed magnetic	**MDLPV3500W**	**CMDLPV3500W**
600	3	Fixed thermal, fixed magnetic	**MDLPV3600W**	**CMDLPV3600W**

Note

① Terminals not included with frames.

Accessories

2

Available Accessories

- Auxiliary switch
- Shunt trip
- Electrical operator
- Alarm lockout
- Undervoltage release
- Terminals
- Lock-off devices
- End cap kits
- Rotary handle mechanisms
- Flexible shaft handle mechanisms

Optional modifications

- Freeze testing

For complete internal and external accessories, see the accessory section of each frame.

External Accessories

Description	Frame	Catalog Number
Imperial Base Mounting Hardware		
0.164-32 x 1.5-inch pan-head steel screws and lockwashers	FD PV	**BMH1**
0.250-20 x 1.5 inch pan-head steel screws and lockwashers	KD PV	**BMH3**
—	LG PV	N/A
0.3125-18 x 1.25 inch filister-head steel screws and lockwashers and flat washers	MDL PV	**BMH5**
Metric Base Mounting Hardware		
M4–0.7 x 38 mm pan-head steel screws and lockwashers	FD PV	**BMH1M**
M6–0.7 x 38 mm pan-head steel screws and lockwashers	KD PV	**BMH3M**
—	LG PV	Included ①
M8-1.25 x 35 mm pan-head steel screws and lockwashers	MDL PV	**BMH5M**
Interphase Barriers		
	FD PV	**IPB1**
	KD PV	**IPB3**
	LG PV	**IPB3**
	MDL PV	**IPB4**
Non-Padlockable Handle Block		
	FD PV	**LKD1**
	KD PV	**LKD3**
	LG PV	N/A
	MDL PV	**LKD4**
Padlockable Handle Lock Hasp ②		
	FD PV	**PLK1**
	KD PV	**PLK3**
	LG PV	**LPHL**
	MDL PV	**HLK4**

Factory Modifications—Freeze Testing to –40°C ③

Frame	Modification Code
FD PV	F01
KD PV	F01
LG PV	F01
MDL PV	F01
Special calibration—contact Eaton for availability	

Molded Case Switches

Eaton's DC molded case switches (MCS) are used in applications requiring a compact, high capacity disconnect. PVGard 1000 Vdc MCS are UL 489B listed and have automatic instantaneous current protection. These devices do not provide overload protection.

Molded Case Switches

Maximum Continuous Ampere Rating at 50 °C	Interrupting Capacity Vdc	Poles in Series	Catalog Number
1000 Vdc Maximum			
100	3000	4	**FDPV4100KW**
200	5000	4	**KDPV4200KW**
250	5000	4	**KDPV4250KW**
350	5000	4	**KDPV4350KW**
400	5000	4	**LGPV4400KSW**
600	7500	3	**MDLPV3600KSW**

Notes

① Base mounting hardware is included with a circuit breaker or a molded case switch (included with breaker). If required separately, order 66A2546G02.

② Locks in ON and OFF position.

③ Add 20% to list price.

Internal Accessories—Right Pole Mounting

	FD PV ①		KD PV		LG PV		MDL PV	
	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number
Auxiliary Switch								
1A-1B	A06	**A1X1PK**	A06	**A1X3PK**	A1	**AUX1A1BPK**	A06	**A1X4PK**
2A-2B	A13	**A2X1RPK**	A13	**A2X3PK**	A2	**AUX2A2BPK**	A13	**A2X4PK**
Alarm Switch								
1 make/1 break	B06	**A1L1RPK**	B06	**A1L3RPK**	B1	**ALM1M1BJPK**	B06	**A1L4RPK**
Auxiliary and Alarm Combo								
1A-1B, 1 make/1 break	C05	**AAL1RPK**	C05	**AAL3RPK**	B2	**AUXALRMJPK**	C05	**AA114RPK**

Internal Accessories—Left Pole Mounting

	FD PV ①		KD PV		LG PV		MDL PV	
	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number	Factory Modification Code	Field Kit Catalog Number
Shunt Trip								
12 Vdc	S02	**SNT1LP03K**	S42	**SNT3P04K**	S4	**SNT012CPK**	S02	**SNT4LP03K**
24 Vdc	S02	**SNT1LP03K**	S42	**SNT3P04K**	S6	**SNT024CPK**	S02	**SNT4LP03K**
48 Vdc	S06	**SNT1LP08K**	S50	**SNT3P06K**	S7	**SNT4860CPK**	S86	**SNT4LP23K**
60 Vdc	S06	**SNT1LP08K**	S50	**SNT3P06K**	S7	**SNT4860CPK**	S86	**SNT4LP23K**
125 Vdc	S10	**SNT1LP12K**	S10	**SNT3P11K**	S2	**SNT120CPK**	S42	**SNT4LP26K**
250 Vdc	S14	**SNT1LP18K**	S14	**SNT3P14K**	—	—	S14	**SNT4LP14K**
120 Vac	S10	**SNT1LP12K**	S10	**SNT3P11K**	S2	**SNT120CPK**	S10	**SNT4LP11K**
Undervoltage Release								
12 Vdc	U30	**UVH1LP20K**	T02	**UVH3LP20K**	U1	**UVR012DPK**	T02	**UVH4LP20K**
24 Vdc	U34	**UVH1LP21K**	T02	**UVH3LP21K**	U2	**UVR024DPK**	T06	**UVH4LP21K**
48 Vdc	U38	**UVH1LP22K**	T10	**UVH3LP22K**	U4	**UVR048DPK**	T10	**UVH4LP22K**
60 Vdc	—	—	—	—	—	—	—	—
125 Vdc	U42	**UVH1LP26K**	T14	**UVH3LP26K**	U6	**UVR125DPK**	T14	**UVH4LP26K**
250 Vdc	U46	**UVH1LP28K**	T18	**UVH3LP28K**	U8	**UVR250DPK**	T18	**UVH4LP28K**
120 Vac	U14	**UVH1LP08K**	U18	**UVH3LP08K**	U5	**UVR120APK**	U18	**UVH4LP08K**

Notes

① Underwriters Laboratories requires that internal accessories for the FD PV be installed at the factory. Internal accessories are UL listed for factory installation under E7819. Where local codes and standards permit and UL listing is not required, internal accessories can be field installed. Accessory installation should be done before the circuit breaker is mounted and connected.

One accessory can be mounted per pole, per breaker.

PVGard Solar Circuit Breaker Terminal Offering

Breaker Frame	Maximum Breaker Ampacity	Terminal Body Material	Wire Type	AWG Wire Range/ Number of Conductors	Metric Wire Range mm^2	Number of Terminals Included	Standard Terminal Catalog Number	Comments
FD PV	50	Steel	Cu/Al	14–4 (1)	2.5–25 (1)	3	**3TA50FB**	
	100	Aluminum	Cu/Al	6–300 kcmil (1)	16–150 (1)	3	**3TA225FDK3**	Includes 3P terminal cover
	100	Aluminum	Cu/Al	6–300 kcmil (1)	16–150 (1)	3	**3TA225FDK**	Includes 3P terminal cover Replacement use only
	100	Copper	Cu	4–4/0 (1)	25–95 (1)	3	**3T225FD**	
JG PVS	250	Aluminum	Cu/Al	#8–350 kcmil (1)	—	—	**TA250FJ**	
	250	Aluminum	Cu/Al	(2) 2/0–(2) 4/0	—	①	**3TA251FJK1**	
	250	Aluminum	Cu/Al	(2) 2/0–(2) 4/0	—	②	**3TA251FJK2**	
	250	Copper	Cu	#4–350 kcmil (1)	—	—	**T250FJ**	
KD PV	225	Aluminum	Cu/Al	3–350 kcmil (1)	35–185 (1)	1	**TA300K**	
	250	Aluminum	Cu/Al	250–500 kcmil (1)	120–240 (1)	1	**TA350K**	
	250	Aluminum	Cu/Al	3/0–250 kcmil (2)	95–120 (1)	4	**4TA400K**	Contains interphase barriers
	250	Aluminum	Cu/Al	2/0–250 kcmil (2) or 2/0–500 kcmil (1)	70–240 (2)	4	**4TA401K**	
	300	Aluminum	Cu/Al	3/0–250 kcmil (2)	95–120 (2)	4	**4TA401K**	Contains interphase barriers
	350	Aluminum	Cu/Al	3/0–250 kcmil (2)	95–120 (2)	4	**4TA401K**	Contains interphase barriers
	225	Copper	Cu	3–350 kcmil (1)	35–185 (1)	1	**T300K**	
	250	Copper	Cu	250–500 kcmil (1)	120–240 (1)	1	**T350K**	
	250	Copper	Cu	3/0–250 kcmil (2)	95–120 (1)	4	**4T400K**	Contains interphase barriers
	300	Copper	Cu	3/0–250 kcmil (2)	95–120 (2)	4	**4TA401K**	Contains interphase barriers
	350	Copper	Cu	3/0–250 kcmil (2)	95–120 (2)	4	**4TA401K**	Contains interphase barriers
LG PV	400	Aluminum	Cu/Al	2–500 kcmil (2)	35–240 (2)	4	**4TA632LK**	Includes 4P terminal cover
	250	Copper	Cu	2–500 kcmil (1)	35–240 (1)	1	**T350LK**	
	400	Copper	Cu	2–500 kcmil (2)	35–240 (2)	4	**4T632LK**	Includes 4P terminal cover
MDL PV	300	Aluminum	Cu/Al	1–500 kcmil (2)	—	1	**TA700MA1**	
	600	Aluminum	Cu/Al	3/0–400 kcmil (3)	—	1	**TA800MA2**	

Endcap Kits

Breaker Frame	Number of Poles	Thread Type	Thread Size	Catalog Number
FD PV	4	Imperial	10–32	**KPEK14**
	4	Metric	M–5	**KPEKM14**
KD PV	4	Imperial	0.312–18	**KPEK34**
	4	Metric	M–8	**KPEKM34**
LG PV	4	Imperial	—	**N/A**
	4	Metric	M-10	**L4RTWK**
MDL PV	3	Imperial	—	—
	3	Metric	—	—

Jumpers

Jumpers must be ordered separately. Priced individually.

FD PV Frame

Description	Maximum Amperes	Catalog Number
Single copper jumper	60	**DC1F060** ①
	100	**DC1F100** ①
	125	**DC1F125** ①
	225	**DC1F225** ①

KD PV Frame

Description	Maximum Amperes	Catalog Number
Single copper jumper	400	**DC1K400** ①

LG PV Frame

Description	Maximum Amperes	Catalog Number
Package of 2 aluminum jumpers	400	**DC2LG400A**
Package of 3 aluminum jumpers	400	**DC3LG400A**
Package of 30 aluminum jumpers	400	**DC30LG400A**

Technical Data and Specifications

- Thermal-magnetic circuit breakers
- Designed to meet UL 489B for solar photovoltaic circuit protection
- 100% rated of the continuous current rating
- 50 °C calibrated
- Can be applied in grounded, ungrounded or bi-polar systems
- Ability to open on signal from DC arc or ground fault detector
- UL File EE350638, Category Control Number DIUR
- 1000 Vdc poles-in-series breaker and switch
  - Requires poles in series connection

Quick Reference PVGard Solar Circuit Breakers 1000 Vdc Poles-in-Series

PVGard 1000 Vdc Current Ratings by Frame UL 489B Interrupting Capacity (kA) 1000 Vdc

Circuit Breaker Type	Minimum Amperes	Maximum Amperes	kA Rating	Poles in Series
FD PV	30	100	3	4
KD PV	125	350	5	4
LG PV	250	400	5	4
MDL PV	300	600	7.5	3

Note

① Not UL Listed; Non UL listed jumpers used in a UL application may need to be qualified by the OEM in their assembly. This may take place with UL or another certified testing agency.

2

PVGard 1000 Vdc Solar PV Circuit Breakers (100% and 80% Rated Frames)

	FD PV	KD PV	LG PV	MDL PV
Number of poles	4	4	4	3
Maximum voltage rating	1000 Vdc	1000 Vdc	1000 Vdc	1000 Vdc
Maximum current rating	100 A	350 A	400 A	600 A
Interrupting capacity at 1000 Vdc	3 kA	5 kA	5 kA	7.5 kA
Time constant	1 ms	1 ms	1 ms	1 ms
Ampere range	15–100 A	125–350 A	250–400 A	300–600 A
Trip unit type	Thermal-magnetic	Thermal-magnetic	Thermal-magnetic	Thermal-magnetic
Rated impulse withstand voltage				
Main conducting paths	8 kV	8 kV	8 kV	8 kV
Auxiliary circuits	4 kV	4 kV	4 kV	4 kV
Endurance				
Mechanical operations	10,000	10,000	8000	8000
Electrical operations	1000	400	400	400
Maximum switching frequency	300 per hour	240 per hour	240 per hour	240 per hour
Third-party certification	UL 489B	UL 489B	UL 489B	UL 489B
Environment				
Design ambient temperature	50 °C	50 °C	50 °C	50 °C
Maximum current at 60 °C, as % of rated current	91%	91%	93%	93%
Maximum current at 70 °C, as % of rated current	88%	88%	88%	88%
Operating temperature range	–20 °C to +50 °C	–20 °C to +50 °C	–20 °C to +50 °C	–20 °C to +50 °C
Storage temperature range	–20 °C to +70 °C	–20 °C to +70 °C	–20 °C to +70 °C	–20 °C to +70 °C
Suitable for freeze temperatures to –40 °C	Option	Option	Option	Option
Relative humidity	0 to 95% noncondensing	0 to 95% noncondensing	0 to 95% noncondensing	0 to 95% noncondensing
Suitable for reverse-feed applications	Yes	Yes	Yes	Yes
Mounting—permissible mounting position				

Connection diagrams



Terminations				
Al/Cu wire	#6–300 kcmil	(2) 3/0–250 kcmil	(2) #2–500 kcmil	(3) 3/0–400 kcmil
Cu wire	#4–4/0	(2) 3/0–250 kcmil	(2) #2–500 kcmil	(3) 3/0–300 kcmil
Dimensions in inches (mm)				
Height	6.00 (152.4)	10.13 (257.3)	10.13 (257.3)	16.00 (406.4)
Width	5.50 (139.7)	7.22 (183.4)	7.22 (183.4)	8.25 (209.5)
Depth	3.38 (85.9)	4.09 (103.9)	4.09 (103.9)	4.06 (103.1)
Weight in lbs	6	20	20	29

Notes

① Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.

② Suitable for use on ungrounded systems only.

Dimensions

Approximate Dimensions in Inches (mm)

PVGard Solar Circuit Breakers—1000 Vdc Poles-in-Series

Frame	Number of Poles	Width	Height	Depth
FD PV	4	5.50 (139.7)	6.00 (152.4)	3.38 (86.0)
KD PV	4	7.22 (183.4)	10.13 (257.3)	4.09 (103.9)
LG PV	4	7.22 (183.4)	10.13 (257.3)	4.09 (103.9)
MDL PV	3	8.25 (209.6)	16.00 (406.4)	4.06 (103.1)

Wiring Diagrams

Series Connection Diagrams for DC Application ①②

FD PV, KD PV, LG PV—1000 Vdc Maximum—Four Poles-in-Series



Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.



Suitable for use on ungrounded systems only.

MDL PV—1000 Vdc Maximum—Three Poles in Series



Suitable for use on ungrounded systems, or grounded systems that have one end of load (A) connected to grounded terminal, opposite poles in series connection.



Suitable for use on ungrounded systems only.

Notes

① Poles in series connection is customer supplied. Use rated cable per NEC.

② For grounded systems, all poles in series must be connected on non-grounded terminal, with load connected to grounded terminal.

E² Mining Service Breakers

Contents

Description	*Page*
Engine Generator Circuit Breakers	**V4-T2-343**
Direct Current Circuit Breakers	**V4-T2-349**
PVGard Solar Circuit Breakers—600 Vdc Per-Pole and 1000 Vdc Poles-in-Series	**V4-T2-363**
E² Mining Service Breakers	
Catalog Number Selection	**V4-T2-374**
Product Selection	**V4-T2-378**
Accessories	**V4-T2-389**
Dimensions	**V4-T2-392**
Classic Mining Breakers	**V4-T2-398**
Add-On Ground Fault Protection—Type GFR	**V4-T2-412**

E² Mining Service Breakers

Product Overview

State-of-the-art E² mining service breakers incorporate the rigid specifications and testing procedures developed by a focus group led by engineers from several large coal companies and Eaton design engineers. Additionally, the performance of these breakers was proven and verified during hundreds of hours of field testing in harsh mine environments.

E² mining breakers are available in 600 Vac, l000Y/577 Vac and 1200 Vac. Interchangeable trip units can be used on either 600 or 1000 Vac frames.

The E² mining breaker family is designed especially for trailing cable application per MSHA 30 CFR 75. Field interchangeable electronic rms sensing trip units are available from 150 to 2000 amperes with instantaneous pickup settings conforming to the code of Federal Regulations 30 CFR 75.601-2. Electromechanical trip units are also available with a wide range of magnetic pickup ranges.

E² electronic trip units are the first to provide the mining industry with true rms sensing, made possible by the custom ASIC microprocessor in each electronic trip unit.

E² breakers are designed to be physically and electrically interchangeable with Classic Mining Service Breakers and supersede Series C® Mining Service Breakers. The table to the right outlines direct replacements.

600 Vac Mining Breaker Replacement Chart

Classic	Series C	E²
FBM	FDBM	E²F
HFBM	FDM	E²F
	HFDM (mag. only)	E²F
—	JDM	E²J
KAM	KDM	E²K
KAMH	KDM	E²K
LAM	LDM	E²L
LAMH	LDM	E²L
LCM	LDM	E²L
LCMH	LDM	E²L
MAM	—	E²M
MAMH	—	E²M
MCM	—	E²M
MCMH	—	E²M
NBM	—	E²N
NBMH	—	E²N
NCM	—	E²N
NCMH	—	E²N

1000 Vac Mining Breaker Replacement Chart

Classic	Series C	E²M
HFM	—	E²FM
—	JDCM	E²JM
HKAM	KDCM	E²KM
HLAM	LDCM	E²LM
HLCM	LDCM	E²LM
HMAM	—	E²MM
HMCM	—	E²MM
HNBM	—	E²NM
HNBMH	—	E²NM
HNCM	—	E²NM
HLCLM	—	E²NM
HPBM	—	E²RM ①

Additional Information on Mining Breakers

Source	Description
TD01217001E	E² Mining Circuit Breaker Dimensional Data
BR01217001E	E² Mining Circuit Breaker Brochure
TC01217001E	E² Mining Circuit Breaker Time Current Curves
www.eaton.com/mining	Mining and Metals

Note

① E²R/E²RM is a new frame physically different than the HPBM. See DS29-170MS.

Eaton's mining service circuit breakers provide short-circuit protection as specified in the code of Federal Regulations 30 CFR 75.601-2.

E^2 225/400 A K frame and 400/600 A L frame electronic trip units feature specifically designed instantaneous pickup settings to conform exactly with the code of Federal Regulations 30 CFR 75.601-2. Electromechanical trip units are also available with a wide range of magnetic pickup ranges.

The tables below list the conductor size maximum allowable circuit breaker instantaneous setting and the E^2 breaker that meets that setting.

Interrupting Capacity Rating

	Interrupting Capacity (Symmetrical kA)					
	Vac (50/60 Hz)					Vdc ①
Circuit Breaker Type	240	480	600	1000Y/577	1200	250
E^2F	65	35	18	—	—	10
E^2J	65	35	18	—	—	10
E^2K	65	35	25	—	—	10
E^2LME	100	65	35	—	—	42
E^2L	65	35	25	—	—	22
E^2M	65	35	25	—	—	22
E^2N	65	50	25	—	—	—
E^2R	125	65	50	—	—	—
E^2FM	65	25	18	10	—	10
E^2JM	65	35	18	10	—	22
E^2KM	65	35	25	14	—	10
E^2LMZ	100	65	35	10	—	42
E^2LM	—	35	25	18	—	22
E^2MM	—	35	25	18	—	22
E^2NM ②	—	50	25	25	—	—
E^2RM	—	65	50	25	—	—
E^2KW	—	—	—	10	10	—
E^2LW	—	—	—	10	10	—
E^2MW	—	—	—	12	12	—

Trailing Cable Setting Per 30 CFR 75

Conductor Size	Maximum Breaker Instantaneous Setting	Maximum Ampere 75 °C Insulated Conductor	E^2/E^2M/E^2W Instantaneous Only	Setting
14	50	15	E^2K 150 A	A
12	75	20	E^2K 150 A	B
10	150	30	E^2K 150 A	C
8	200	50	E^2K 225 A	A
6	300	65	E^2K 225 A	B
4	500	85	E^2K 225 A / E2L 400 A	C/A
3	600	100	E^2K 225 A / E2L 400 A	D/B
2	800	115	E^2K 225 A / E2L 400 A	E/C
1	1000	130	E^2K 225 A / E2L 400 A	F/D
1/0	1250	150	E^2K 225 A / E2L 400 A	G/E
2/0	1500	175	E^2K 225 A / E2L 400 A	H/F
3/0	2000	200	E^2L 400 A	G
4/0	2500	230	E^2L 400 A	H
250	2500	255	E^2L 400 A	H
300	2500	285	E^2L 400 A	H
350	2500	310	E^2L 400 A	H
400	2500	335	E^2L 400 A	H
500	2500	380	E^2L 400 A	H

Auxiliary Switch Electrical Rating Data

Maximum Voltage	Frequency	Maximum Current Amperes
600	50/60 Hz	6.0
125	DC	0.5 (non-inductive load)
250	DC	0.25 (non-inductive load)

Alarm (Signal/Lockout Switch) Electrical Rating Data

Maximum Voltage	Frequency	Maximum Current Amperes
600	50/60 Hz	6.0
125	DC	0.5 (non-inductive load)
250	DC	0.25 (non-inductive load)

Notes

① Two poles in series. DC rating applies to breakers with thermal-magnetic trip unit. Breakers with electronic trip units are not DC rated.

② Series rated for application with Eaton's E^2KM and E^2LM breakers.

Catalog Number Selection

This information is presented only as an aid to understanding catalog numbers.
It is not to be used to build catalog numbers for circuit breakers or trip units.

2

E² Mining Service Breaker with 310+ Electronic Trip Unit Technology

E2K E M 3 400 38 2 B20 W

Frame Size
- E2K
- E2L
- E2M
- E2N
- E2R

Electronic Trip
- E ① = Electronic trip

Voltage
- Blank = 600 Vac max.
- M = 1000Y/577 Vac max.

Number of Poles
- 3 = Three-pole

Current Ampere Rating
- 100–2000

Trip Unit Function
- M = 310+ Electronic Inst only (magnetic only)
- Blank = 310+ Electronic LSI
- 38 = 310+ Electronic ALSI with maintenance mode

Magnetic Rating (If Applicable)
- Blank = Standard mag.
- 2 = High mag.

Optional Features
- B20 ② = High load alarm

Terminal
- W = No terminals
- Blank = Standard terminals

E² Mining Service 310+ Electronic Trip Unit

K E M 3 400 38 T 2 B20

Frame Size
- K
- L
- M

Electronic Trip
- E = Electronic trip

Voltage
- M = 600 V and 1000 V interchangeable

Number of Poles
- 3 = Three-pole

Current Ampere Rating
- 100–2000

Trip Unit Function
- M = 310+ Electronic Inst only (magnetic only)
- Blank = 310+ Electronic LSI
- 38 = 310+ Electronic ALSI with maintenance mode

Trip Unit
- T

Magnetic Rating (If Applicable)
- Blank = Standard mag.
- 2 = High mag.

Optional Features
- B20 ① = High load alarm

Notes

① All N- and R-Frame breakers equipped with 310+ Electronic Trip Unit. No "E" suffix required.
② Not available with instantaneous only.

E² Mining Service Breaker Frame Only ①



E² Mining Service Breaker with Thermal-Magnetic Trip Unit ①



E² Mining Service Thermal-Magnetic Trip Unit ①



Notes

① Does not apply to E2LME/LMZ.

② Only available in K-, L- and M-Frames.

Undervoltage Release Mechanism Electrical Rating Data

Breaker Type	Supply Voltage	Dropout Voltage Minimum	Dropout Voltage Maximum	Pickup Voltage Maximum	VA
E^2F/E^2FM	110 Vac	44.5	77	93.5	1.3
	120 Vac				1.5
	127 Vac				1.7
	110 Vdc				1.5
	120 Vdc				1.7
	125 Vdc				1.9
E^2J/E^2JM	110 Vac	44.5	77	93.5	1.8
	120 Vac				2.1
	127 Vac				2.4
	110 Vdc				1.6
	120 Vdc				1.9
	125 Vdc				2.2
$E^2K/E^2KM/E^2KW$	110 Vac	44.5	77	93.5	1.8
	120 Vac				2.1
	127 Vac				2.4
	110 Vdc				1.6
	120 Vdc				1.9
	125 Vdc				2.2
E^2LME/E^2LMZ	110 Vac	44.5	77	93.5	0.96
	120 Vac				1.13
	127 Vac				1.25
	110 Vdc	43.8	77	93.5	0.94
	120 Vdc				1.12
	125 Vdc				1.21
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	110 Vac	44.5	77	93.5	1.8
	120 Vac				2.1
	127 Vac				2.4
	110 Vdc				1.6
	120 Vdc				1.9
	125 Vdc				2.2
E^2N/E^2NM	110 Vac	44.5	77	93.5	1.8
	120 Vac				2.1
	127 Vac				2.4
	110 Vdc				1.6
	120 Vdc				1.9
	125 Vdc				2.2
E^2R/E^2RM	110 Vac	44.5	77	93.5	3.3
	120 Vac				3.6
	127 Vac				3.8
	110 Vdc	43.8	77	93.5	3.3
	120 Vdc				3.6
	125 Vdc				3.8

Shunt Trip Electrical Rating Data

Breaker Type	Supply Voltage	Operating Voltage Minimum	VA
E^2F/E^2FM	48 Vac	33.6	92
	60 Vac		140
	110 Vac		480
	120 Vac		570
	127 Vac		640
	208 Vac	146	180
	220 Vac		200
	230 Vac		240
	48 Vdc	33.6	100
	60 Vdc		160
	110 Vdc	77	55
	120 Vdc		66
	125 Vdc		71
E^2J/E^2JM	110 Vac	60.5	66
	120 Vac		84
	127 Vac		102
	110 Vdc	77	112
	120 Vdc		138
	125 Vdc		150
$E^2K/E^2KM/E^2KW$	110 Vac	60	100
	120 Vac		120
	127 Vac		140
	110 Vdc	77	110
	120 Vdc		130
	125 Vdc		140
	24 Vac		41
	48 Vac	18	139
	60 Vac		210
E^2LME/E^2LMZ	110 Vac	60	83
	120 Vac		92
	127 Vac		117
	24 Vdc		120
	48 Vdc	18	475
	60 Vdc		720
	110 Vdc	82	99
	120 Vdc		120
	125 Vdc		121

Breaker Type	Supply Voltage	Operating Voltage Minimum	VA
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	48 Vac	34	830
	60 Vac		1280
	110 Vac	60	100
	120 Vac		120
	127 Vac		140
	48 Vdc	34	710
	60 Vdc		1105
	110 Vdc	77	110
	120 Vdc		130
	125 Vdc		140
E^2N/E^2NM	110 Vac	60	100
	120 Vac		120
	127 Vac		140
	110 Vdc	77	110
	120 Vdc		130
	125 Vdc		140
E^2R/E^2RM	110 Vac	60.5	330
	120 Vac		390
	127 Vac		430
	110 Vdc	77	370
	120 Vdc		440
	125 Vdc		480

Product Selection

3 A–150 A

E²F/E²FM

E²F/E²FM

Sealed Breakers with Non-Interchangeable Trip Unit—Include Line/Load Terminals, Non-Electronic Trip Units ①

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 10 kA at 1000 Vac Three-Pole Complete Breaker Catalog Number
Thermal-Magnetic				
15	—	—	**E2F3015**	—
20	—	—	**E2F3020**	**E2FM3020**
25	—	—	**E2F3025**	**E2FM3025**
30	—	—	**E2F3030**	—
35	—	—	**E2F3035**	—
40	—	—	**E2F3040**	**E2FM3040**
45	—	—	**E2F3045**	—
50	—	—	**E2F3050**	**E2FM3050**
60	—	—	**E2F3060**	**E2FM3060**
70	—	—	**E2F3070**	**E2FM3070**
80	—	—	**E2F3080**	**E2FM3080**
90	—	—	**E2F3090**	**E2FM3090**
100	—	—	**E2F3100**	**E2FM3100**
125	—	—	**E2F3125**	**E2FM3125**
150	—	—	**E2F3150**	**E2FM3150**
Magnetic Only				
3	9–30	—	**E2F003AM**	—
7	21–70	—	**E2F007CM**	—
15	45–150	—	**E2F015EM**	—
30	90–300	—	**E2F030HM**	—
	50–150	—	**E2F030EM**	—
50	150–500	—	**E2F050KM**	**E2FM050KM**
	66–190	—	**E2F050YM**	**E2FM050YM**
70	210–700	—	**E2F070MM**	**E2FM070MM**
100	150–500	—	**E2F100KM**	**E2FM100KM**
	300–1000	—	**E2F100RM**	**E2FM100RM**
150	450–1500	—	**E2F150TM**	**E2FM150TM**
	750–2500	—	**E2F150UM**	**E2FM150UM**

Note

① For two-pole application, use outer poles.

70 A–250 A

E²J/E²JM

E²J/E²JM

Circuit Breakers with Interchangeable Non-Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 10 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number
Thermal-Magnetic				
70	300–650	**E2J3070T**	**E2J3070W**	**E2JM3070W**
90	450–900	**E2J3090T**	**E2J3090W**	**E2JM3090W**
100	500–1000	**E2J3100T**	**E2J3100W**	**E2JM3100W**
125	625–1250	**E2J3125T**	**E2J3125W**	**E2JM3125W**
150	750–1500	**E2J3150T**	**E2J3150W**	**E2JM3150W**
175	875–1750	**E2J3175T**	**E2J3175W**	**E2JM3175W**
200	1000–2000	**E2J3200T**	**E2J3200W**	**E2JM3200W**
225	300–650	**E2J3225TA**	**E2J3225AW**	**E2JM3225AW**
	500–1000	**E2J3225TD**	**E2J3225DW**	**E2JM3225DW**
	1125–2250	**E2J3225T**	**E2J3225W**	**E2JM3225W**
250	1250–2500	**E2J3250T**	**E2J3250W**	**E2JM3250W**
Magnetic Only				
250	300–650	**E2J3250TMA**	**E2J3250MAW**	**E2JM3250MAW**
	450–900	**E2J3250TMC**	**E2J3250MCW**	**E2JM250MCW**
	500–1000	**E2J3250TMD**	**E2J3250MDW**	**E2JM3250MDW**
	625–1250	**E2J3250TMF**	**E2J3250MFW**	**E2JM3250MFW**
	750–1500	**E2J3250TMG**	**E2J3250MGW**	**E2JM3250MGW**
	875–1750	**E2J3250TMJ**	**E2J3250MJW**	**E2JM3250MJW**
	1000–2000	**E2J3250TMK**	**E2J3250MKW**	**E2JM3250MKW**
	1125–2250	**E2J3250TML**	**E2J3250MLW**	**E2JM3250MLW**
	1250–2500	**E2J3250TM**	**E2J3250MW**	**E2JM3250MW**

Notes

① Frame only: **E2J3250F**.

② Frame only: **E2JM3250F**.

100 A–400 A

E²K/E²KM/E²KW

2

E²K/E²KM

Circuit Breakers with Interchangeable Non-Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 14 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number	1200 Vac Maximum 10 kA at 1200 Vac Three-Pole ③④ Complete Breaker Catalog Number
Thermal-Magnetic					
100	500–1000	**E2K3100T**	**E2K3100W**	**E2KM3100W**	**E2KW3100W**
125	625–1250	**E2K3125T**	**E2K3125W**	**E2KM3125W**	**E2KW3125W**
150	750–1500	**E2K3150T**	**E2K3150W**	**E2KM3150W**	**E2KW3150W**
175	875–1750	**E2K3175T**	**E2K3175W**	**E2KM3175W**	**E2KW3175W**
200	1000–2000	**E2K3200T**	**E2K3200W**	**E2KM3200W**	**E2KW3200W**
225	300–650	**E2K3225TA**	**E2K3225AW**	**E2KM3225AW**	**E2KW3225AW**
	500–1000	**E2K3225TD**	**E2K3225DW**	**E2KM3225DW**	**E2KW3225DW**
	1125–2250	**E2K3225T**	**E2K3225W**	**E2KM3225W**	**E2KW3225W**
250	1250–2500	**E2K3250T**	**E2K3250W**	**E2KM3250W**	**E2KW3250W**
300	1500–3000	**E2K3300T**	**E2K3300W**	**E2KM3300W**	**E2KW3300W**
320	1600–3200	—	—	—	**E2KW3320W**
350	1750–3500	**E2K3350T**	**E2K3350W**	**E2KM3350W**	**E2KW3350W**
400	2000–4000	**E2K3400T**	**E2K3400W**	**E2KM3400W**	—
Magnetic Only					
400	300–650	**E2K3400TMA**	**E2K3400MAW**	**E2KM3250MAW**	**E2KW3250MAW**
	500–1000	**E2K3400TMD**	**E2K3400MDW**	**E2KM3400MDW**	**E2KW3350MDW**
	625–1250	**E2K3400TMF**	**E2K3400MFW**	**E2KM3400MFW**	**E2KW3350MFW**
	750–1500	**E2K3400TMG**	**E2K3400MGW**	**E2KM3400MGW**	**E2KW3350MGW**
	875–1750	**E2K3400TMJ**	**E2K3400MJW**	**E2KM3400MJW**	**E2KW3350MJW**
	1000–2000	**E2K3400TMK**	**E2K3400MKW**	**E2KM3400MKW**	**E2KW3350MKW**
	1125–2250	**E2K3400TML**	**E2K3400MLW**	**E2KM3400MLW**	**E2KW3350MLW**
	1250–2500	**E2K3400TMW**	**E2K3400MWW**	**E2KM3400MWW**	**E2KW3350MWW**
	1500–3000	**E2K3400TMN**	**E2K3400MNW**	**E2KM3400MNW**	**E2KW3350MNW**
	1600–3200	—	—	—	**E2KW3350MVW**
	1750–3500	**E2K3400TMR**	**E2K3400MRW**	**E2KM3400MRW**	**E2KW3350MRW**
	2000–4000	**E2K3400TM**	**E2K3400MW**	**E2KM3400MW**	—

Notes

① Frame only: **E2K3400F**.

② Frame only: **E2KM3400F**.

③ 1200 V breakers are sold as “complete breakers” only.

④ Maximum continuous ampere rating at 50 °C.

Please see TD01217001E for detailed dimensions.

100 A–400 A

E²KE/E²KEM

E²KM

Circuit Breakers with Interchangeable Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/577 Vac Maximum 250 Vdc 14 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number
310+ Electronic Instantaneous Only				
150	50–800	**KEM3150TM**	**E2KE3150MW**	**E2KEM3150MW**
225	200–1500	**KEM3225TM**	**E2KE3225MW**	**E2KEM3225MW**
	500–2500	**KEM3225TM2**	**E2KE3225M2W**	**E2KEM3225M2W**
400	200–1500	**KEM3400TM**	**E2KE3400MW**	**E2KEM3400MW**
	500–2500	**KEM3400TM2**	**E2KE3400M2W**	**E2KEM3400M2W**
310+ Electronic LSI ③				
100	50–800	**KEM3100T**	**E2KE3100W**	**E2KEM3100W**
125	50–800	**KEM3125T**	**E2KE3125W**	**E2KEM3125W**
150	50–800	**KEM3150T**	**E2KE3150W**	**E2KEM3150W**
200	200–1500	**KEM3200T**	**E2KE3200W**	**E2KEM3200W**
225	200–1500	**KEM3225T**	**E2KE3225W**	**E2KEM3225**
	500–2500	**KEM3225T2**	**E2KE32252W**	**E2KEM32252W**
400	200–1500	**KEM3400T**	**E2KE3400W**	**E2KEM3400W**
	500–2500	**KEM3400T2**	**E2KE34002W**	**E2KEM34002W**
310+ Electronic ALSI with Maintenance Mode ③				
100	50–800	**KEM310038T**	**E2KE310038W**	**E2KEM310038W**
125	50–800	**KEM312538T**	**E2KE312538W**	**E2KEM312538W**
150	50–800	**KEM315038T**	**E2KE315038W**	**E2KEM315038W**
200	200–1500	**KEM320038T**	**E2KE320038W**	**E2KEM320038W**
225	200–1500	**KEM322538T**	**E2KE322538W**	**E2KEM322538**
	500–2500	**KEM322538T2**	**E2KE3225238W**	**E2KEM3225238W**
400	200–1500	**KEM340038T**	**E2KE340038W**	**E2KEM340038W**
	500–2500	**KEM340038T2**	**E2KE3400238W**	**E2KEM3400238W**

Notes

① Frame only: **E2K3400F**.

② Frame only: **E2KM3400F**.

③ For High Load Alarm option (B20): **E2KE340038B20W, KEM3400TB20**.

Please see TD01217001E for detailed dimensions.

160 A–400 A

E²LME/E²LMZ (Series G)

Circuit Breakers

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 14 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number
Magnetic Only				
400	3600–4400	**LT3400KM**	**E2LME3400KMW**	**E2LMZ3400KMW**
Interchangeable Electronic Trip Unit				
160	320–1920	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
200	400–2400	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
225	450–2700	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
250	500–3000	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
300	600–3600	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
315	630–3780	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
350	700–4200	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**
400	800–4800	**LT340031M**	**E2LME340031W**	**E2LMZ340031W**

Notes

① Frame only: **E2LME3400NN**.

② Frame only: **E2LMZ3400NN**.

Please see TD01217001E for detailed dimensions.

300 A–600 A

E²L/E²LM/E²LW

Circuit Breakers with Interchangeable Non-Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number	1200 Vac Maximum 10 kA at 1200 Vac Three-Pole ③ Complete Breaker Catalog Number
Thermal-Magnetic					
300	1500–3000	**E2L3300T**	**E2L3300W**	**E2LM3300W**	**E2LW3300W**
320	2250–4500	**E2L3450T**	**E2L3450W**	**E2LM3450W**	**E2LW3320W**
350	1600–3200	—	—	—	**E2LW3350W**
400	1750–3500	**E2L3350T**	**E2L3350W**	**E2LM3350W**	**E2LW3400W**
450	2000–4000	**E2L3400T**	**E2L3400W**	**E2LM3400W**	**E2LW3450W**
500	2500–5000	**E2L3500T**	**E2L3500W**	**E2LM3500W**	—
600	3000–6000	**E2L3600T**	**E2L3600W**	**E2LM3600W**	—
	1125–2250	**E2L3600TL** ④	—	—	—
Magnetic Only					
450	1600–3200	—	—	—	**E2LW3450MVW**
	1125–2250	—	—	—	**E2LW3450MLW**
	1500–3000	—	—	—	**E2LW3450MNW**
	1750–3500	—	—	—	**E2LW3450MRW**
	2000–4000	—	—	—	**E2LW3450MXW**
	2250–4500	—	—	—	**E2LW3450MYW**
600	1125–2250	**E2L3600TML**	**E2L3600MLW**	**E2LM3600MLW**	—
	1500–3000	**E2L3600TMN**	**E2L3600MNW**	**E2LM3600MNW**	—
	1750–3500	**E2L3600TMR**	**E2L3600MRW**	**E2LM3600MRW**	—
	2000–4000	**E2L3600TMX**	**E2L3600MXW**	**E2LM3600MXW**	—
	2250–4500	**E2L3600TMY**	**E2L3600MYW**	**E2LM3600MYW**	—
	2500–5000	**E2L3600TMP**	**E2L3600MPW**	**E2LM3600MPW**	—
	3000–6000	**E2L3600TM**	**E2L3600MW**	**E2LM3600MW**	—

Notes

① Frame only: **E2L3600F**.
② Frame only: **E2LM3600F**.
③ Maximum continuous ampere rating at 50 °C.
④ 600 A thermal 1125–2250 T.A.

Please see TD01217001E for detailed dimensions.

300 A–600 A

E²LE/E²LEM

2

E²LM

Circuit Breakers with Interchangeable Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number
310+ Electronic Instantaneous Only				
400	500–2500	**LEM3400TM**	**E2LE3400MW**	**E2LEM3400MW**
	1000–4000	**LEM3400TM2**	**E2LE3400M2W**	**E2LEM3400M2W**
600	500–2500	**LEM3600TM**	**E2LE3600MW**	**E2LEM3600MW**
	2500–5000	**LEM3600TM2**	**E2LE3600M2W**	**E2LEM3600M2W**
310+ Electronic LSI ③				
300	500–2500	**LEM3300T**	**E2LE3300W**	**E2LEM3300W**
350	500–2500	**LEM3350T**	**E2LE3350W**	**E2LEM3350W**
400	500–2500	**LEM3400T**	**E2LE3400W**	**E2LEM3400W**
	1000–4000	**LEM3400T2**	**E2LE34002W**	**E2LEM34002W**
600	500–2500	**LEM3600T**	**E2LE3600W**	**E2LEM3600W**
	2500–5000	**LEM3600T2**	**E2LE36002W**	**E2LEM36002W**
310+ Electronic ALSI with Maintenance Mode ③				
300	500–2500	**LEM330038T**	**E2LE330038W**	**E2LEM330038W**
350	500–2500	**LEM335038T**	**E2LE335038W**	**E2LEM335038W**
400	500–2500	**LEM340038T**	**E2LE340038W**	**E2LEM340038W**
	1000–4000	**LEM340038T2**	**E2LE3400238W**	**E2LEM3400238W**
600	500–2500	**LEM360038T**	**E2LE360038W**	**E2LEM360038W**
	2500–5000	**LEM360038T2**	**E2LE3600238W**	**E2LEM3600238W**

Notes

① Frame only: **E2L3600F**.

② Frame only: **E2LM3600F**.

③ For High Load Alarm option (B20): **E2LE360038B20W, LEM3600TB20**.

Please see TD01217001E for detailed dimensions.

300 A— 800 A

E²M/E²MM/E²MW

E²M/E²MM/E²MW

Circuit Breakers with Interchangeable Non-Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number	1200 Vac Maximum 12 kA at 1200 Vac Three-Pole ③④ Complete Breaker Catalog Number
Thermal-Magnetic					
400	1000–2000	—	—	—	**E2MW3400W**
500	1250–2500	—	—	—	**E2MW3500W**
600	1500–3000	**E2M3600TN**	**E2M3600W**	**E2MM3600W**	**E2MW3600W**
630	1600–3200	—	—	—	**E2MW3630W**
800	2000–4000	**E2M3800TX**	**E2M3800W**	**E2MM3800W**	**E2MW3800W**
Magnetic Only					
800	1500–3000	**E2M3800TMN**	**E2M3800MNW**	**E2MM3800MNW**	**E2MW3800MNW**
	1600–3200	—	—	—	**E2MW3800MVW**
	2000–4000	**E2M3800TMX**	**E2M3800MXW**	**E2MM3800MXW**	**E2MW3800MXW**
	2500–5000	**E2M3800TMP**	**E2M3800MPW**	**E2MM3800MPW**	—
	3000–6000	**E2M3800TMW**	**E2M3800MWW**	**E2MM3800MWW**	—

Notes

① Frame only: **E2M3800F**.
② Frame only: **E2MM3800F**.
③ 1200 V breakers are sold as “complete breakers” only.
④ Maximum continuous ampere rating at 50 °C.

Please see TD01217001E for detailed dimensions.

800 A

E²ME/E²MEM

2

E²MN

Circuit Breakers with Interchangeable Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole ① Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole ② Complete Breaker Catalog Number
310+ Electronic Instantaneous Only				
800	500–2500	**MEM3800TM**	**E2ME3800MW**	**E2MEM3800MW**
	1000–4000	**MEM3800TM2**	**E2ME3800M2W**	**E2MEM3800M2W**
310+ Electronic LSI ③				
800	500–2500	**MEM3800T**	**E2ME3800W**	**E2MEM3800W**
	1000–4000	**MEM3800T2**	**E2ME38002W**	**E2MEM38002W**
310+ Electronic ALSI with Maintenance Mode ③				
800	500–2500	**MEM380038T**	**E2ME380038W**	**E2MEM380038W**
	1000–4000	**MEM380038T2**	**E2ME3800382W**	**E2MEM3800382W**

Notes

① Frame only: **E2M3800F**.
② Frame only: **E2MM3800F**.
③ For High Load Alarm option (B20): **E2ME380038B20W, MEM3800TB20**.

Please see TD01217001E for detailed dimensions.

400 A–1200 A

E²N/E²NM

E²NM

Circuit Breakers with Interchangeable Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole Complete Breaker Catalog Number
310+ Electronic Instantaneous Only				
800	500–2500	—	**E2N3800MW**	**E2NM3800MW**
1200	1250–5000	—	**E2N312MW**	**E2NM312MW**
310+ Electronic LSI ①				
400	500–2500	—	**E2N3400W**	**E2NM3400W**
500	500–2500	—	**E2N3500W**	**E2N3M500W**
600	500–2500	—	**E2N3600W**	**E2NM3600W**
700	500–2500	—	**E2N3700W**	**E2NM3700W**
800	500–2500	—	**E2N3800W**	**E2NM3800W**
900	1250–5000	—	**E2N3900W**	**E2NM3900W**
1000	1250–5000	—	**E2N310W**	**E2NM310W**
1200	1250–5000	—	**E2N312W**	**E2NM312W**
310+ Electronic ALSI with Maintenance Mode ①				
400	500–2500	—	**E2N340038W**	**E2NM340038W**
500	500–2500	—	**E2N350038W**	**E2NM350038W**
600	500–2500	—	**E2N360038W**	**E2NM360038W**
700	500–2500	—	**E2N370038W**	**E2NM370038W**
800	500–2500	—	**E2N380038W**	**E2NM380038W**
900	1250–5000	—	**E2N390038W**	**E2NM390038W**
1000	1250–5000	—	**E2N31038W**	**E2NM31038W**
1200	1250–5000	—	**E2N31238W**	**E2NM31238W**

Notes

① For High Load Alarm option (B20): **E2N380038B20W**.

Please see TD01217001E for detailed dimensions.

1600 A–2000 A

E²R/E²RM

2

E²RM

Circuit Breakers with Electronic Trip Units

Maximum Continuous Ampere Rating at 40 °C	Magnetic Trip Range	Trip Unit Only Catalog Number	600 Vac Maximum 250 Vdc 35 kA at 480 Vac Three-Pole Complete Breaker Catalog Number	1000Y/ 577 Vac Maximum 250 Vdc 18 kA at 1000 Vac Three-Pole Complete Breaker Catalog Number
310+ Electronic LSI ①				
1600	2–8 x I_n	—	**E2R316W**	**E2RM316W**
2000	2–8 x I_n	—	**E2R320W**	**E2RM320W**
310+ Electronic ALSI with Maintenance Mode ①				
1600	2–8 x I_n	—	**E2R31638W**	**E2RM31638W**
2000	2–8 x I_n	—	**E2R32038W**	**E2RM32038W**

Notes

① For High Load Alarm option (B20): **E2R1638B20W**.

Please see TD01217001E for detailed dimensions.

Accessories

Line and Load Terminals

Breaker Type	Maximum Breaker Amperes	Wire Type	AWG Wire Range (No. Conductors)	Catalog Number
E^2F/E^2FM	100	Cu/Al	#14–1/0 (1)	**3T100FB** (package of three)
	150	Cu	#4–4/0 (1)	**3T150FB** (package of three)
E^2J/E^2JM	250	Cu	#4–350 (1)	**T250KB**
$E^2K/E^2KM/E^2KW$	225	Cu	#3–350 (1)	**T300K**
	350	Cu	250–500 (1)	**T350K**
	400	Cu	2/0–250 (2)	**3T400K** (three-pole kit)
E^2LME/E^2LMZ	400	Cu/Al	500–750 (1)	**3TA631LK**
$E^2L/E^2LM/E^2LW$	400	Cu/Al	4/0–600 (1)	**3TA401LDK** (three-pole kit)
	600	Cu	250–350 (2)	**T602LD**
$E^2M/E^2MM/E^2MW$	600	Cu	(2) 2/0–500 kcmil	**T600MA1**
	600	Cu/Al	(2) 1–500 kcmil	**TA700MA1**
	800 std.	Cu/Al	(3) 3/0–400 kcmil	**TA800MA2**
	800	Cu/Al	(2) 500–750 kcmil	**TA801MA**
	800	Cu	(3) 3/0–300 kcmil	**T800MA1**
E^2N/E^2NM	700	Cu	2/0–500 (2)	**T700NB1**
	1000	Cu	3/0–500 (3)	**T1000NB1**
	1200	Cu	3/0–400 (4)	**T1200NB3**
	1600	Cu/Al	500–1000 (4)	**TA1600RD**
	2000	Cu/Al	2–600 (6)	**TA2000RD**

End Cap Terminals—For Use with Ring Type Terminals

Breaker Type	Maximum Breaker Amperes	Catalog Number	Metric Catalog Number	Imperial
E^2F/E^2FM	150	**KPEK1**	**KPEMK1**	—
E^2J/E^2JM	250	**KPEK2**	**KPEMK2**	—
$E^2K/E^2KM/E^2KW$	400	**KPEK3**	**KPEMK3**	—
E^2LME/E^2LMZ	400	—	**L3RTWK**	—
$E^2L/E^2LM/E^2LW$	600	**KPEK4**	**KPEMK4**	—

External Accessories

Padlockable Handle Lock Hasp

Breaker Type	Catalog Number
E^2F/E^2FM	**PLK1**
E^2J/E^2JM	**PLK3**
$E^2K/E^2KM/E^2KW$	**PLK3**
E^2LME/E^2LMZ	**LPHL**
$E^2L/E^2LM/E^2LW$	**HLK4**
$E^2M/E^2MM/E^2MW$	**HLK4**
E^2N/E^2NM	**PLK5**
E^2R/E^2RM	**HLK6**

Internal Accessories

2

Undervoltage Release ①

Breaker Type	UVR Type	Voltage Rating	Mounting Location	Catalog Number	Factory Modification Code
E^2F/E^2FM	Handle reset	208–240 Vac	Left pole	**UVH1LP11K** (thermal/magnetic only) ②	U18
	Handle reset	110–127 Vdc	Left pole	**UVH1LP26K** (thermal/magnetic only) ②	U42
E^2J/E^2JM	Handle reset	110–127 Vac	Left pole	**UVH2LP08K** ②	U18
	Handle reset	208–240 Vac	Left pole	**UVH2LP11K** ②	U22
	Handle reset	110–125 Vdc	Left pole	**UVH2LP26K** ②	T14
$E^2K/E^2KM/E^2KW$	120 volt handle reset with LED	120 Vac	Left pole	**UVM3LP08K** ②③	U66
	120 volt handle reset with LED	120 Vac	Left pole	**UVM3LP08KT** ②④	U68
	Handle reset	110–127 Vac	Left pole	**UVH3LP08K** ②	U18
	Handle reset	208–240 Vac	Left pole	**UVH3LP11K** ②	U22
	Handle reset	110–125 Vdc	Left pole	**UVH3LP26K** ②	T14
E^2LME/E^2LMZ	Handle reset	110–127 Vac	Left pole	**UVR120APK**	U5
	Handle reset	110–125 Vdc	Left pole	**UVR125DPK**	U6
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	120 volt handle reset with LED	120 Vac	Left pole	**UVM4LP08K** ②③	U66
	120 volt handle reset with LED	120 Vac	Left pole	**UVM4LP08KT** ②④	U68
	Handle reset	110–127 Vac	Left pole	**UVH4LP08K** ②	U18
	Handle reset	208–240 Vac	Left pole	**UVH4LP11K** ②	U22
	Handle reset	110–125 Vdc	Left pole	**UVH4LP26K** ②	T14
E^2N/E^2NM	120 volt handle reset with LED	120 Vac	Left pole	**UVM5LP08K** ③	U66
	120 volt handle reset with LED	120 Vac	Left pole	**UVM5LT08K** ④	U68
	Handle reset	110–127 Vac	Left pole	**UVH5LP08K** ②	U18
	Handle reset	208–240 Vac	Left pole	**UVH5LP11K** ②	U22
	Handle reset	110–125 Vdc	Left pole	**UVH5LP26K** ②	T14
E^2R/E^2RM	120 volt handle reset with LED	120 Vac	Right pole	**UVM6RP08K** ③⑤	U58
	Handle reset	110–127 Vac	Right pole	**UVH6RP08K** ⑤	U49
	Handle reset	208–240 Vac	Right pole	**UVH6RP11K** ⑤	U53
	Handle reset	110–125 Vdc	Right pole	**UVH6RP26K** ⑤	T33

Notes

① Contact Eaton for internal accessory voltage ratings not listed.
② LH (RH also available).
③ Pigtail leads.
④ Terminal blocks.
⑤ RH only.

Shunt Trip ①

Breaker Type	Voltage Rating	Mounting Location	Catalog Number	Factory Modification Code
E^2F/E^2FM	48–127 Vac or 48–60 Vdc	Left pole	**SNT1LP08K** ②	S06
	208–230 Vac or 110–127 Vdc	Left pole	**SNT1LP12K** ②	S10
E^2J/E^2JM	110–240 Vac or 110–125 Vdc	Left pole	**SNT2P11K** ③	S10
$E^2K/E^2KM/E^2KW$	110–240 Vac or 110–125 Vdc	Left pole	**SNT3P11K** ③	S10
E2LME/E2LMZ	24 Vac/Vdc	Left pole	**SNT024CPK**	S6
	48–60 Vac/Vdc	Left pole	**SNT4860CPK**	S7
	110–240 Vac/Vdc	Left pole	**SNT120CPK**	S2
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	48–60 Vac	Left pole	**SNT4LP05K** ②	S06
	48–60 Vdc	Left pole	**SNT4LP23K** ②	S86
	110–240 Vac	Left pole	**SNT4LP11K** ②	S10
	110–125 Vdc	Left pole	**SNT4LP26K** ②	S42
E^2N/E^2NM	110–240 Vac	Left pole	**SNT5LP11K** ②	S10
	110–125 Vdc	Left pole	**SNT5LP26K** ②	S42
E^2R/E^2RM	110–240 Vac	Right pole	**SNT6P11K** ④	S29
	110–125 Vdc	Right pole	**SNT6P26K** ④	S45

Auxiliary Switch

Breaker Type	Number of Sets of Contacts (1A and 1B)	Mounting Location	Catalog Number	Factory Modification Code
E^2F/E^2FM	1	Right	**A1X1PK**	A06
	2	Right	**A2X1RPK**	A13
E^2J/E^2JM	1	Right	**A1X2PK**	A06
	2	Right	**A2X2PK**	A13
$E^2K/E^2KM/E^2KW$	1	Right	**A1X3PK**	A06
	2	Right	**A2X3PK**	A13
E^2LME/E^2LMZ	1	Right	**AUX1A1BPK**	A1
	2	Right	**AUX2A2BPK**	A2
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	1	Right	**A1X4PK**	A06
	2	Right	**A2X4PK**	A13
E^2N/E^2NM	1	Right	**A1X5PK**	A06
	2	Right	**A2X5PK**	A13
E^2R/E^2RM	2	Right	**A2X6RPK**	A12
	4	Right	**A4X6RPK**	A19

Alarm (Signal/Lockout Switch)

Breaker Type	Number of Sets of Contacts (Make and Break)	Mounting Location	Catalog Number	Factory Modification Code
E^2F/E^2FM	1	Right	**A1L1LPK/A1L1RPK**	B06
	2	Right	**A2L1LPK/A2L1RPK**	B13
E^2J/E^2JM	1	Right	**A1L2LPK/A1L2RPK**	B06
$E^2K/E^2KM/E^2KW$	1	Right	**A1L3LPK/A1L3RPK**	B06
	2	Right	**A2L3LPK/A2L3RPK**	B13
E^2LME/E^2LMZ	1	Right	**ALM1M1BJPK**	B1
	2	Right	**ALM2M2BJPK**	B3
$E^2L/E^2LM/E^2LW/E^2M/E^2MM/E^2MW$	1	Right	**A1L4LPK/A1L4RPK**	B06
	2	Right	**A2L4LPK/A2L4RPK**	B13
E^2N/E^2NM	1	Right	**A1L5LPK/A1L5RPK**	B06
	2	Right	**A2L5LPK/A2L5RPK**	B13
E^2R/E^2RM	1	Right	**A1L6RPK**	B05
	2	Right	**A2L6RPK**	B12

Notes

① Contact Eaton for internal accessory voltage ratings not listed.
② LH (RH also available).
③ LH or RH.
④ RH only.

Dimensions

Approximate Dimensions in Inches (mm)

2

Please see TD01217001E for detailed dimensions.

3 A–150 A

E^2F/E^2FM
Sealed Breakers with Non-Interchangeable Trip Unit—Include Line/Load Terminals Non-Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	4.13 (104.9)
B	6.00 (152.4)
C	3.38 (85.9)
D	3.50 (88.9)

70 A–250 A

E^2J/E^2JM
Circuit Breakers with Interchangeable Non-Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	4.13 (104.9)
B	10.00 (254.0)
C	4.06 (103.1)
D	4.31 (109.5)

Approximate Dimensions in Inches (mm)

Please see TD01217001E for detailed dimensions.

100 A–400 A

$E^2K/E^2KM/E^2KW$
Circuit Breakers with Interchangeable Non-Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	5.49 (139.4)
B	10.13 (257.3)
C	4.06 (103.1)
D	4.31 (109.5)

100 A–400 A

E^2KE/E^2KEM
Circuit Breakers with Interchangeable Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	5.49 (139.4)
B	10.13 (257.3)
C	4.06 (103.1)
D	4.31 (109.5)

Approximate Dimensions in Inches (mm)

Please see TD01217001E for detailed dimensions.

2

160 A–400 A

E^2LME/E^2LMZ Circuit Breakers



Front View Side View

Description	Dimensions in Inches (mm)
A	5.48 (139.2)
B	10.13 (257.3)
C	4.00 (101.6)
D	4.22 (107.1)

300 A–600 A

$E^2L/E^2LM/E^2LW$ Circuit Breakers with Interchangeable Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	8.25 (209.6)
B	10.75 (273.1)
C	4.06 (103.1)
D	4.38 (111.3)

Approximate Dimensions in Inches (mm)

Please see TD01217001E for detailed dimensions.

300 A–600 A

E^2LE/E^2LEM
Circuit Breakers with Interchangeable Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	8.25 (209.6)
B	10.75 (273.1)
C	4.06 (103.1)
D	4.38 (111.3)

300 A–800 A

$E^2M/E^2MM/E^2MW$
Circuit Breakers with Interchangeable Non-Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	8.25 (209.6)
B	16.00 (406.4)
C	4.06 (103.1)
D	4.38 (111.3)

Approximate Dimensions in Inches (mm)

Please see TD01217001E for detailed dimensions.

2

800 A

E^2ME/E^2MEM
Circuit Breakers with Interchangeable Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	8.25 (209.6)
B	16.00 (406.4)
C	4.06 (103.1)
D	4.38 (111.3)

400 A–1200 A

E^2N/E^2NM
Circuit Breakers with Interchangeable Electronic Trip Units



Front View Side View

Description	Dimensions in Inches (mm)
A	8.25 (209.6)
B	16.00 (406.4)
C	5.50 (139.7)
D	6.00 (152.4)

Approximate Dimensions in Inches (mm)

Please see TD01217001E for detailed dimensions.

1600 A–2000 A

E^2R/ E^2RM
Circuit Breakers with Electronic Trip Units



Front View **Side View**

Description	Dimensions in Inches (mm)
A	15.50 (393.7)
B	16.00 (406.4)
C	9.00 (228.6)
D	10.00 (254.0)

2

Contents

Description	*Page*
Engine Generator Circuit Breakers	**V4-T2-343**
Direct Current Circuit Breakers	**V4-T2-349**
PVGard Solar Circuit Breakers—600 Vdc Per-Pole and 1000 Vdc Poles-in-Series	**V4-T2-363**
E^2 Mining Service Breakers	**V4-T2-372**
Classic Mining Breakers	
Product Selection	**V4-T2-400**
Accessories	**V4-T2-405**
Reference Information	**V4-T2-407**
Add-On Ground Fault Protection—Type GFR	**V4-T2-412**

Classic Mining Breakers

Product Overview

Classic mining service circuit breakers continue to be manufactured and are primarily applied to achieve an exact physical and electronic replacement of previously Cutler-Hammer installed Westinghouse equipment. To upgrade to the current offering of E^2 mining circuit breakers, consult the cross reference information on **Page V4-T2-407.**

AC Interrupting Capacity, Symmetrical Amperes

	Breaker Type				
60 Hz AC Volts	**KAM**	**LAM, MAM, NBM**	**HKAM**	**HLAM** ②	**All Other 1000 Volt Breakers** ②
240	25,000	42,000	—	—	—
480	22,000	30,000	—	—	—
600	22,000	22,000	—	—	—
1000 ①	—	—	10,000	12,000	14,000

Special DC Interrupting Capacity

		Interrupting Capacity (Amperes) at 300–330 Vdc			
		Single-Pole		Two Poles in Series ④	
Breaker Type	**Maximum Ampere Rating**	**0.0–0.15 mH Inductance** ③	**0.15–0.5 mH Inductance**	**0.5–0.9 mH Inductance**	**2.4 mH Inductance**
KAM	225	15,000	10,000	15,000	5000
LAM	400/600	15,000	10,000	15,000	5000
MAM	800	15,000	10,000	15,000	5000
NBM	1200	15,000	10,000	15,000	5000

Notes

① Based on circuit power factor of 50% or greater.
② HLAM must be rear stud connected. If front connected, interrupting capacity rating is 10,000 amperes.
③ Resistive circuit.
④ Two poles in electrical series in ungrounded leg of circuit.

Classic Circuit Breakers For Mining Service

Undervoltage Release Data

Undervoltage releases are calibrated to pick up at 72 to 85% of rated voltage dropout between 35 to 70% of rated voltage.

Breaker Type	Volts	Line Amperes	Series Resistors ①	Total VA
KAM, HKAM ①	480/60	0.021	10,000	10.1
	240/60	0.019	—	4.6
	120/60	0.021	—	2.5
	120/60 ②	0.13	—	15.6
LAM, HLAM, MAM, HMAM, NBM, HNBM ①	480/60	0.033	12,000 ③	15.9
	240/60	0.028	6,000	6.7
	120/60	0.029	—	3.5
	120/60 ②	0.13	—	15.6

Shunt Trip Coil Data

Breaker Type	Volts	Amperes	VA
KAM, HKAM, LAM, HLAM, MAM, HMAM, NBM, HNBM	480/60	0.085	40.8
	240/60	1.7	408
	120/60	0.88	105.6
	48 DC	8.0	384

Notes

① Supplied for external customer mounting.
② New design electrical reset UVR.
③ 16,000 for Type MAM and HMAM.

Product Selection

For reference only. Replace these frames with E2 Series. See Cross-Reference information beginning on **Page V4-T2-407**.

Classic Mining Service Circuit Breakers

Breaker Type	Frame Style Numbers ①②	Poles	Amperes	Trip Type	Accessories (Included in Frame)	Magnetic Trip Range, Amperes ③
KAM	**2609D60G64**	2	180	M	None	200–400
	1291C26G07	2	180	M	UVR ④	200–400
	2609D60G66	2	180	M	Standard shunt trip ③	200–400
	1291C26G01	2	225	TM	UVR ④	300–700
	1291C26G02	2	225	TM	UVR ④	500–1000
	2609D60G67	3	180	M	None	200–400
	1291C26G08	3	180	M	UVR ④	200–400
	2609D60G69	3	180	M	Standard shunt trip ③	200–400
	5685D48G75	3	225	TM	None	300–700
	5685D48G74	3	225	TM	None	500–1000
	1291C26G03	3	225	TM	UVR ④	300–700
	1291C26G04	3	225	TM	UVR ④	500–1000
	2609D60G01	3	225	TM	Standard shunt trip ③	300–700
	2609D60G02	3	225	TM	Standard shunt trip ③	500–1000
	2609D60G40	3	225	M	None	300–700
	2609D60G41	3	225	M	None	500–700
	1291C26G05	3	225	M	UVR ④	300–700
	1291C26G06	3	225	M	UVR ④	500–1000
LAM	**1291C32G01**	2	400	TM	UVR ④	500–1000
	2609D60G61	2	400	M	Shunt trip (48 Vdc)	750–1500
	1291C32G03	3	400	TM	UVR ④	500–1000
	5685D48G73	3	400	TM	None	800–1600
	1291C32G02	3	400	TM	UVR ④	800–1600
	2609D60G03	3	400	TM	Standard shunt trip ③	800–1600
	2609D60G44	3	400	M	None	800–1600
	1291C32G04	3	400	M	UVR ④	800–1600

Notes

① Terminals not included in style number.

② All breakers listed are complete with accessories indicated.

③ Rated 120 volts/60 Hz: undervoltage release is handle reset type.

④ UVR is auto-reset type, 120 Vac.

M = magnetic only; TM = thermal-magnetic.

For reference only. Replace these frames with E2 Series. See Cross-Reference information beginning on **Page V4-T2-407**.

Classic Mining Service Circuit Breakers, continued

Breaker Type	Frame Style Numbers ①②	Poles	Amperes	Trip Type	Accessories (Included in Frame)	Magnetic Trip Range, Amperes ③
MAM	**2609D60G17**	2	600	TM	UVR ③	750–1500
	2609D60G18	2	800	TM	UVR ③	1000–2000
	2609D60G63	3	400	TM	UVR ③	2000–4000
	5685D48G72	3	600	TM	None	1500–3000
	2609D60G19	3	600	TM	UVR ③	1500–3000
	2609D60G04	3	600	TM	Standard shunt trip ③	1500–3000
	2609D60G05	3	800	TM	Standard shunt trip ③	2000–4000
	5685D48G71	3	800	TM	None	2000–4000
	2609D60G20	3	800	TM	UVR ③	2000–4000
	2609D60G46	3	800	M	None	1500–3000
	2609D60G47	3	800	M	UVR ③	1500–3000
	2609D60G48	3	800	M	None	2000–4000
	2609D60G49	3	800	M	UVR ③	2000–4000
NBM	**1229C37G13**	2	1000	TM	UVR ④	1500–3000
	1229C37G14	2	1200	TM	UVR ④	2000–4000
	1227C36G10	3	1000	TM	None	2500–5000
	1229C37G15	3	1000	TM	UVR ④	2500–5000
	1227C36G13	3	1000	TM	Standard shunt trip ③	2500–5000
	1227C36G14	3	1200	TM	Standard shunt trip ③	2500–5000
	1227C36G09	3	1200	TM	None	2500–5000
	1229C37G16	3	1200	TM	UVR ④	2500–5000
	1227C36G19	3	1200	M	None	2500–5000
	1229C37G17	3	1200	M	UVR ④	2500–5000

Notes

① Terminals not included in style number.
② All breakers listed are complete with accessories indicated.
③ Rated 120 volts/60 Hz: undervoltage release is handle reset type.
④ UVR is auto-reset type, 120 Vac.

M = magnetic only; TM = thermal-magnetic.

1000 Volt Classic Mining Service Circuit Breakers

	Breaker Type	Frame Style Numbers	Poles	Amperes	Trip Type	Accessories (Included in Frame)	Magnetic Trip Range, Amperes ①
HKAM	HKAM	**2609D60G70**	3	180	M	None	200–400
		1291C26G16	3	180	M	UVR ②	200–400
		5685D48G87	3	225	TM	None	300–700
		1291C26G12	3	225	TM	UVR ②	300–700
		5685D48G86	3	225	TM	None	500–1000
		1291C26G13	3	225	TM	UVR ②	500–1000
		1291C26G14	3	225	M	UVR ②	300–700
		1291C26G15	3	225	M	UVR ②	500–1000
HLAM	HLAM	**5685D48G85**	3	400	TM	None	800–1600
		1291C32G07	3	400	TM	UVR ②	800–1600
		1291C32G09	3	400	M	UVR ②	800–1600
HMAM	HMAM	**5685D48G84**	3	600	TM	None	1500–3000
		2609D60G28	3	600	TM	UVR ③	1500–3000
		5685D48G83	3	800	TM	None	2000–4000
		2609D60G29	3	800	TM	UVR ③	2000–4000
		2609D60G57	3	800	M	UVR ③	1500–3000
		2609D60G58	3	800	M	UVR ③	2000–4000
HNAM	HNBM	**1227C36G12**	3	1000	TM	None	2500–5000
		1229C37G19	3	1000	TM	UVR ②	2500–5000
		1227C36G11	3	1200	TM	None	2500–5000
		1229C37G20	3	1200	TM	UVR ②	2500–5000
		1229C37G18	3	1200	M	UVR ②	2500–5000

Notes

① The magnetic trip range does not change when rating plug is changed.

② 120 volt, 60 Hz electrical reset type.

③ Rated 120 volts, 60 Hz; undervoltage release is handle reset type.

M = magnetic only; TM = thermal-magnetic.

Classic Mining Service Breaker Frames Only

Breaker Type	Frame Size, Amperes	Number of Poles	Style Numbers
KAM ①	225	2	**2602D86G11**
	225	3	**2602D86G12**
KAMH ①	225	2	**2602D86G13**
	225	3	**2602D86G14**
HKAM ①	225	3	**1264C99G05**
LAM ②	400	2	**2602D99G05**
	400	3	**2602D99G06**
LAMH ②	400	2	**2602D99G07**
	400	3	**2602D99G08**
HLAM ②	400	3	**1264C99G02**
LAM3600F	600	3	**2603D48G07**
LAMH3600F	600	3	**2603D48G08**
HLAM3600F	600	3	**2603D48G09**

Breaker Type	Frame Size, Amperes	Number of Poles	Style Numbers
MAM ②	800	2	**2600D43G11**
	800	3	**2600D43G12**
MAMH ②	800	2	**2600D43G13**
	800	3	**2600D43G14**
HMAM ②	800	3	**1264C99G03**
NBM ②	1200	2	**2610D64G07**
	1200	3	**2610D64G08**
NBMH ②	1200	2	**2610D64G09**
	1200	3	**2610D64G10**
HNBM ②	1200	3	**2610D64G13**

Trip Units for Classic Mining Circuit Breakers

Breaker Type	Conductor Size	Magnetic Trip Range, Amperes	Maximum Continuous Amperes	Thermal-Magnetic Three-Pole ③ Style Numbers	Magnetic Only Three-Pole Style Numbers
HKAM	#6	150–400	180	—	**2609D99G22**
	#4–#3	300–700	225	**5685D48G40**	**2611D75G01**
	#4–#1	500–1000	225	**5685D48G34**	**2611D75G02**
HLAM	#4–#1	750–1500	400	**5685D48G97**	**2609D99G21**
	#2–#2/0	800–1600	400	**5685D48G28**	**2611D75G03**
HLAM600	#2–2/0	750–1500	600	**2609D99G20**	—
	2/0–500 kcmil	1500–3000	600	**2609D99G19**	—
HMAM	#2–#2/0	750–1500	600	—	—
	2/0–500 kcmil	1500–3000	600	**5685D48G22**	**2611D75G04** ④
	#1–3/0	1000–2000	800	—	—
	3/0–500 kcmil	2000–4000	800	**5685D48G16**	**2611D75G05**
HNBM	2/0–500 kcmil	1500–3000	1000	—	—
	4/0–500 kcmil	2500–5000	1000	**5685D48G10**	—
	3/0–500 kcmil	2000–4000	1200	—	—
	4/0–500 kcmil	2500–5000	1200	**5685D48G04**	**2611D75G07**

Notes

① Frame modified for left-hand mounting of UVR attachment.
② Frame modified for right-hand mounting of UVR attachment.
③ Three-pole trip units only are suitable for replacement in 1000 volt mining service circuit breakers.
④ 800 amperes.

Terminals For Classic Mining Service Breakers

Terminals are UL listed for wire type and range listed below.
When used with aluminum conductors, use joint compound.

Breaker Type	Terminal Type	Maximum Amperes	Package of 3 Line Terminals Style Number	Wire Range, Type
FBM, HFBM	Style pressure type terminals	100	**624B100G02**	#14–1/0 Al/Cu
	Optional Al/Cu pressure terminals	50	**624B100G10**	#14–#4 Al/Cu
		100	**624B100G17**	# 4–4/0 Al/Cu

Terminals For Mining Service Breakers

Breaker Type	Terminal Type	Maximum Amperes	Terminal Catalog Number	Wire Range, Type Number of Cables
KAM, HKAM	Standard pressure terminals (copper only)	225	**T225LA**	(1) #6–350 kcmil
	Optional Al/Cu pressure terminals	225	**TA225LA1**	(1) #6–350 kcmil Cu, or (1) #4–350 kcmil Al
LAM	Standard copper pressure terminals	225	**T225LA**	(1) #6–350 kcmil Cu
		400	**T401LA**	(1) #4–250 kcmil Cu plus (1) 3/0–600 kcmil Cu
	Optional Al/Cu pressure terminals	225	**TA225LA1**	(1) #6–350 kcmil Cu, or (1) #4–350 kcmil Al
		400	**TA400LA1**	(1) #4–250 kcmil Al/Cu, plus (1) 3/0–600 kcmil Al/Cu
		400	**TA401LA**	(1) 600–750 kcmil Al
LAM-600, LAMH-600, HLAM-600	Standard copper pressure terminals	600	**T600LA**	(2) 250–500 kcmil Cu
	Optional Al/Cu pressure terminals	600	**TA600LA**	(2) 250–500 kcmil Al/Cu
MAM, HMAM, MAMH	Standard copper pressure terminals	350	**T350MA**	(1) #1–600 kcmil Cu
		600	**T600MA1**	(2) 2/0–500 kcmil Cu
		800	**T800MA1**	(3) 3/0–300 kcmil Cu
	Optional Al/Cu pressure terminals	600	**TA700MA1**	(2) #1–500 kcmil Al/Cu
		800	**TA800MA2**	(3) 3/0–400 kcmil Al/Cu
		800	**TA801MA**	(2) 500–750 kcmil Al/Cu
NBM, HNBM, NBMH	Standard copper pressure terminals	1000	**T1000NB1**	(3) 3/0–500 kcmil Cu
		1200	**T1200NB1**	(4) 3/0–400 kcmil Cu
	Optional Al/Cu pressure terminals	1000	**TA1000NB1**	(3) 3/0–400 kcmil Al/Cu
		1200	**TA1200NB1**	(4) 4/0–500 kcmil Al/Cu
		1200	**TA1201NB1**	(3) 500–750 kcmil Al/Cu

Accessories

Classic Mining Circuit Breakers

Rear Connected Studs ①

For complete stud assembly, order a stud and tube based on thickness of customer's mounting panel. A short stud must be assembled adjacent to a long stud to maintain clearances required by Underwriters Laboratories.② Two studs required per pole. For List Prices, see Eaton's Price and Availability Digest.

Mounting Panel Thickness In Inches (mm)	Stud Length	Stud Style Numbers	Tube Length In Inches (mm)	Tube Style Numbers
KAM, HKAM Breakers				
0.75 (19.1)–1.00 (25.4)	Short	**656D565G01**	0.84 (21.3)	**456D983H05**
	Long	**656D565G02**	3.78 (96.0)	**456D983H08**
0.50 (12.7)–0.75 (19.1)	Short	**656D565G01**	1.09 (27.7)	**456D983H06**
	Long	**656D565G02**	4.03 (102.4)	**456D983H09**
0.25 (6.4)–0.50 (12.7)	Short	**656D565G01**	1.34 (34.0)	**456D983H07**
	Long	**656D565G02**	4.28 (108.7)	**456D983H10**

Rear Connected Studs For Insulated Panels Only: Two Per Pole

Stud Ampere Number	Diameter, In Inches (mm) and Thread	Extension Back of Breaker In Inches (mm)	Stud Style Numbers
LAM, HLAM Breakers			
225 ③	0.50 (12.7)–13	3.22 (81.8)	**1241 345**
	0.50 (12.7)–13	6.28 (159.5)	**1241 346**
225 ③④	0.50 (12.7)–13	4.97 (126.2)	**1241 392**
400 ③	0.75 (19.1)–16	5.47 (138.9)	**05B7383G22**
	0.75 (19.1)–16	7.97 (202.4)	**05B7383G23**
	0.75 (19.1)–16	10.47 (265.9)	**05B7383G24**
600	1.00 (25.4)–12	5.91 (150.1)	**314C960G16**
	1.00 (25.4)–12	8.41 (213.6)	**314C960G17**
	1.00 (25.4)–12	10.91 (277.1)	**314C960G18**
MAM, HMAM, MAMH Breakers			
225	0.50 (12.7)–13	3.66 (93.0)	**314C960G01**
400	0.75 (19.1)–16	5.91 (150.1)	**314C960G04**
	0.75 (19.1)–16	8.41 (213.6)	**314C960G05**
	0.75 (19.1)–16	10.91 (277.1)	**314C960G06**
600	1.00 (25.4)–12	5.91 (150.1)	**314C960G07**
	1.00 (25.4)–12	8.41 (213.6)	**314C960G08**
	1.00 (25.4)–12	10.91 (277.1)	**314C960G09**
800	1.13 (28.7)–12	4.91 (124.7)	**314C960G10**
	1.13 (28.7)–12	8.41 (213.6)	**314C960G11**
	1.13 (28.7)–12	10.91 (277.1)	**314C960G12**
NBM, HNBM, NBMH Breakers			
800	1.13 (28.7)–12	5.50 (139.7)	**623B222G01**
	1.13 (28.7)–12	8.00 (203.2)	**623B222G02**
	1.13 (28.7)–12	10.50 (266.7)	**623B222G03**
1200	1.25 (31.8)–12	5.50 (139.7)	**373B375G04**
	1.25 (31.8)–12	10.50 (266.7)	**373B375G03**

Line and Load Terminal Shields ⑤

Breaker Type	Description	Style Numbers
KAM	Line terminals	**1261C93G01**
	Load terminals	**1262C46G01**
LAM-400	Line terminals	**1261C95G01**
	Load terminals	**1262C48G01**
MAM	Line terminals	**1261C97G01**
	Load terminals	**1261C97G02**

Notes

① Not UL listed.
② 400 ampere LA studs of the same length have sufficient clearance; however, customer connections may make it necessary to use a short stud adjacent to a long stud.
③ 150, 300 and 400 ampere frames only.
④ This is a special stud that includes six contact nuts for use where bus contact nuts must be used.
⑤ For breakers used with terminals and cable connections. Sold in packages of 10.

Standard Handle Reset Undervoltage Release

For Classic breakers field mountable on special frames listed on **Page V4-T2-407**, or replacement on breakers originally equipped with this type UVR.

For undervoltage protection. A solenoid device mounts within breaker case. Coil must be energized before closing breaker. Trips breaker when voltage drops below 35 to 70% of coil rating. Picks up and seals in at 72 to 85% of coil rating. For line voltages up to 250 Vdc or 600 Vac. Externally mounted resistors are supplied for certain ratings. Standard leads extend 18.00 inches (457.2 mm) outside of breaker. Longer leads may be specified.

Breaker Type	Volts	Style Numbers
Right-Hand Mounting		
LAM, HLAM	120 Vac	**4995D12G11**
	120 Vac ①	**1228C76G03**
	240 Vac	**4995D12G13**
	480 Vac	**4995D12G14**
	125 Vdc	**4995D12G09**
MAM, HMAM, MAMH	120 Vac	**5672D69G11**
	120 Vac ①	—
	240 Vac	**5672D69G13**
	480 Vac	**5672D69G14**
NBM, HNBM, NBMH	120 Vac	**4995D11G11**
	120 Vac ①	**1229C35G03**
	240 Vac	**4995D11G13**
	480 Vac	**4995D11G14**
Left-Hand Mounting		
KAM, HKAM	120 Vac	**4995D10G01**
	120 Vac ①	**1228C76G03**
	240 Vac	**4995D10G03**
	480 Vac	**4995D10G04**

Shunt Trips

For tripping breaker from a remote point. A solenoid device mounts within breaker case. Breaker trips when coil is energized. A cutoff switch breaks the circuit to the momentary rated coil when breaker opens. Available for control voltages up to 250 Vdc or 600 Vac. Voltage and frequency must be specified. Standard leads extend 18.00 inches (457.2 mm) outside of breaker. Longer leads may be specified.

Breaker Type	Volts (50–60 Hz)	Style Numbers
Right-Hand Mounting		
KAM, HKAM	480 Vac	**2605D15G16**
	240 Vac	**2605D15G17**
	120 Vac	**2605D15G19**
LAM, HLAM	480 Vac	**2606D56G16**
	240 Vac	**2606D56G17**
	120 Vac	**2606D56G19**
	48 Vdc	**2606D56G07**
MAM, HMAM, MAMH	480 Vac	**2606D57G16**
	240 Vac	**2606D57G17**
	120 Vac	**2606D57G19**
NBM, HNBM, NBMH	480 Vac	**2606D58G16**
	240 Vac	**2606D58G17**
	120 Vac	**2606D58G19**
Left-Hand Mounting		
KAM, HKAM	480 Vac	**2605D15G02**
	240 Vac	**2605D15G03**
	120 Vac	**2605D15G05**
LAM, HLAM	480 Vac	**2606D56G02**
	240 Vac	**2606D56G03**
	120 Vac	**2606D56G05**
MAM, HMAM, MAMH	480 Vac	**2606D57G02**
	240 Vac	**2606D57G03**
	120 Vac	**2606D57G05**
NBM, HNBM, NBMH	480 Vac	**2606D58G02**
	240 Vac	**2606D58G03**
	120 Vac	**2606D58G05**

Notes

① Electrical reset UVR.

② Auto reset type.

Reference Information

E² Cross-Reference

Series C Mining	Superseded by E² Mining
1491D72G31	E2J3070T
1491D72G32	E2J3090T
1491D72G33	E2J3100T
1491D72G37	E2J3200T
6622C87G27	E2K3225AWU66
6622C87G28	E2K3225DWU66
6622C87G32	E2K3400GWU66
E2KM3100	E2KEM3100W
E2KM3100U66	E2KEM3100WU66
E2KM3125	E2KEM3125W
E2KM3125U66	E2KEM3125WU66
E2KM3150	E2KEM3150W
E2KM3150MU66	E2KEM3150WU66
E2KM3150TM	E2KEM3150MW
E2KM3150U66	E2KEM3150MWU66
E2KM3200	E2KEM3200W
E2KM3200U66	E2KEM3200WU66
E2KM3225	E2KEM3225W
E2KM3225F	E2KM3400F
E2KM3225FUV	E2KM3400F
E2KM3225MU66	E2KEM3225MWU66
E2KM3225TM	E2KEM3225TM
E2KM3225U66	E2KEM3225WU66
E2LM3300U66	E2LEM3300WU66
E2LM3350U66	E2LEM3350WU66
E2LM34002U66	E2LEM34002WU66
E2LM3400F	E2LM3600F
E2LM3400FUV	E2LM3600F
E2LM3400M2U66	E2LEM3400M2WU66
E2LM3400MU66	E2LEM3400MWU66
E2LM3400U66	E2LEM3400WU66
FDBM3015	E2F3015
FDBM3015WU62	E2F3015WU62
FDBM3020	E2F3020
FDBM3025	E2F3025
FDBM3025U62	E2F3025U62
FDBM3030	E2F3030
FDBM3030U62	E2F3030WU62
FDBM3030WU62	E2F3030WU62
FDBM3035	E2F3035

Series C Mining	Superseded by E² Mining
FDBM3040	E2F3040
FDBM3045	E2F3045
FDBM3050	E2F3050
FDBM3050U62	E2F3050U62
FDBM3050WU62	E2F3050WU62
FDBM3060	E2F3060
FDBM3070	E2F3070
FDBM3070WU62	E2F3070WU62
FDBM3080	E2F3080
FDBM3090	E2F3090
FDBM3100	E2F3100
FDBM3100LM04U62	E2F3100M04U62
FDBM3125	E2F3125
FDBM3150	E2F3150
FDBM3150L	E2F3150L
FDM3015	E2F3015
FDM3015L	E2F3015L
FDM3015LU62	E2F3015LU62
FDM3020	E2F3020
FDM3020LU62	E2F3020LU62
FDM3025	E2F3025
FDM3025L	E2F3025L
FDM3025LS22	E2F3025LS22
FDM3025LU62	E2F3025LU62
FDM3030	E2F3030
FDM3030LS22	E2F3030LS22
FDM3040	E2F3040
FDM3040L	E2F3040L
FDM3040LU62	E2F3040LU62
FDM3050	E2F3050
FDM3050LU62	E2F3050LU62
FDM3050U62	E2F3050U62
FDM3060	E2F3060
FDM3060LU62	E2F3060LU62
FDM3070	E2F3070
FDM3070A02U62	E2F3070A02U62
FDM3080	E2F3080
FDM3090	E2F3090
FDM3100	E2F3100
FDM3100LS22	E2F3100LS22

E² Cross-Reference, continued

Series C Mining	Superseded by E² Mining
FDM3100LU62	E2FLU62
FDM3125	E2F3125
FDM3125LU62	E2F3125LU62
FDM3150	E2F3150
HFDM003AM	E2F003AM
HFDM003AMLU62	E2F003AMLU62
HFDM007CM	E2F007CM
HFDM007CMU62	E2F007CMU62
HFDM015EM	E2F015EM
HFDM015EMA02	E2F015EMA02
HFDM015EMLU62	E2F015EMLU62
HFDM015EMU62	E2F015EMU62
HFDM030HM	E2F030HM
HFDM030HMLU62	E2F030HMLU62
HFDM030HMU62	E2F030HMU62
HFDM050KM	E2F050KM
HFDM050KML	E2F050KML
HFDM050KMLU62	E2F050KMLU62
HFDM050KMU62	E2F050KMU62
HFDM070MM	E2F070MM
HFDM070MMU62	E2F070MMU62
HFDM1001M	E2F1001M
HFDM1001MS22	E2F1001MS22
HFDM100LM	E2F100LM
HFDM100LMA02	E2F100LMA02
HFDM100LMU62	E2F100LMU62
HFDM 100RM	E2F100RM
HFDM100RML	E2F100RML
HFDM100RMS22	E2F100RMS22
HFDM100RMU62	E2F100RMU62
HFDM150TM	E2F150TM
HFDM150TML	E2F150TML
HFDM150TMU62	E2F150TMU62
HFDM150UM	E2F150UM
JCDA2D1S30	E2JM250MDA2D1S30
JCMA2D1S30	E2JM250MFA2D1S30
JDCM3070W	E2JM3070W
JDCM3090W	E2JM3090W
JDCM3100W	E2JM3100W
JDCM3125W	E2JM3125W

Series C Mining	Superseded by E² Mining
JDCM3150W	E2JM3150W
JDCM3175W	E2JM3175W
JDCM3200W	E2JM3200W
JDCM3225A5W	E2JM3225AW
JDCM3225D5W	E2JM3225DW
JDCM3225W	E2JM3225W
JDCM3250A5MW	E2JM3250MAW
JDCM3250A5MWU18	E2JM3250MAWU18
JDCM3250A5W	E2JM3250AW
JDCM3250C5MW	E2JM3250MCW
JDCM3250D5MW	E2JM3250MDW
JDCM3250D5MWA06	E2JM3250MDWA06
JDCM3250D5W	E2JM3250DW
JDCM3250D5WS10	E2JM3250DWS10
JDCM3250F	E2JM3250F
JDCM3250F5MD01	E2JM3250MFD01
JDCM3250F5MW	E2JM3250MFW
JDCM3250G5MW	E2JM3250MGW
JDCM3250G5WA02D01	E2JM3250MGA02D01
JDCM3250J5MW	E2JM3250MJW
JDCM3250J5MWA02	E2JM3250MJA02
JDCM3250J5WA02D01	E2JM3250MJA02D01
JDCM3250J5WD01	E2JM3250MJD01
JDCM3250K5MW	E2JM3250MKW
JDCM3250L5MW	E2JM3250MLW
JDCM3250MW	E2JM3250MW
JDCM3250W	E2JM3250W
JDCMAA2D1	E2JM3250MM02D01
JDCMDD1S30	E2JM3250MDS30D01
JDCMFD01	E2JM3250MFD01
JDCMGA02D1	E2JM3250MGA02D01
JDCMJA2D1	E2JM3250MJA02D01
JDCMJD01	E2JM3250MJD01
JDM2250F	E2JM3250F
JDM3070W	E2J3070W
JDM3090W	E2J3090W
JDM3100W	E2J3100W
JDM3125W	E2J3125W
JDM3150W	E2J3150W
JDM3150WU18	E2J3150WU18

E² Cross-Reference, continued

Series C Mining	Superseded by E² Mining
JDM3175W	E2J3175W
JDM3200W	E2J3200W
JDM3200WA06	E2J3200WA06
JDM3225A5W	E2J3225AW
JDM3225D5W	E2J3225DW
JDM3225W	E2J3225W
JDM3250A5MW	E2J3250MAW
JDM3250A5W	E2J3250AW
JDM3250C5MW	E2J3250CW
JDM3250D5MW	E2J3250MDW
JDM3250D5W	E2J3250DW
JDM3250F	E2J3250F
JDM3250F5MW	E2J3250MFW
JDM3250G5MW	E2J3250MGW
JDM3250J5MW	E2J3250MJW
JDM3250K5MW	E2J3250MKW
JDM3250L5MW	E2J3250MLW
JDM3250MW	E2J3250MW
JDM3250W	E2J3250W
JDM3250WS10	E2J3250WS10
JM2225T1125-2250	E2J3225T
JM3070T	E2J3070T
JM3090T	E2J3090T
JM3100T	E2J3100T
JM3125T	E2J3125T
JM3150T	E2J3150T
JM3175T	E2J3175T
JM3200T	E2J3200T
JM3225T	E2J3225T
JM3225TA5	E2J3225TA
JM3225TD5	E2J3225TD
JM3250T	E2J3250T
JM3250TA5	E2J3250TA
JM3250TA5M_350-700	E2J3250TMA
JM3250TC5M	E2J3250TMC
JM3250TD5_500-1000	E2J3250TMD
JM3250TF5M_625-1250	E2J3250TMF
JM3250TG5M_750-1500	E2J3250TMG
JM3250TJ5M_875-1750	E2J3250TMJ
JM3250TK5M_1000-2000	E2J3250TMK

Series C Mining	Superseded by E² Mining
JM3250TL5M_1125-2250	E2J3250TML
JM3250TM	E2J3250TM
KDCM3100W	E2KM3100W
KDCM3125W	E2KM3125W
KDCM3150W	E2KM3150W
KDCM3175W	E2KM3175W
KDCM3200W	E2KM3200W
KDCM3225A5MW	E2KM3200MAW
KDCM3225D5MW	E2KM3200MDW
KDCM3225W	E2KM3225W
KDCM3250W	E2KM3250W
KDCM3250WU18	E2KM3250WU18
KDCM3300W	E2KM3300W
KDCM3350W	E2KM3350W
KDCM3400D5MA02D09H04	E2KM3400MDA02D09H04
KDCM3400D5MW	E2KM3400MDW
KDCM3400D5MWA02D07	E2KM3400MDA02D07
KDCM3400D5W	E2KM3400DW
KDCM3400D5WD09	E2KM3400DD09
KDCM3400F	E2KM3400F
KDCM3400F5MW	E2KM3400MFW
KDCM3400FD09G04	E2KM3400MFD09G04
KDCM3400G5MW	E2KM3400MGD09G05
KDCM3400G5MWD09H04	E2KM3400MGD09H04
KDCM3400G5W	E2KM3400MGW
KDCM3400G5WD07	E2KM3400MGD07
KDCM3400J5MA02D09	E2KM3400MJA02D09
KDCM3400J5MA2D9G4S30	E2KM3400MJA2D9G4S30
KDCM3400J5MD09	E2KM3400MJD09
KDCM3400J5MD09H04S30	E2KM3400MJD09H04S30
KDCM3400J5MW	E2KM3400MJW
KDCM3400J5MWA02D07	E2KM3400MJA02D07
KDCM3400J5MWA06	E2KM3400MJWA06
KDCM3400J5MWD07S30	E2KM3400MJD07S30
KDCM3400J5WD07	E2KM3400MJD07
KDCM3400K5MW	E2KM3400MKW
KDCM3400K5MWS10	E2KM3400MKWS10
KDCM3400K5MWU18	E2KM3400MKWU18
KDCM3400L5MW	E2KM3400MLW
KDCM3400L5MWD09H04	E2KM3400MLD09H04

E² Cross-Reference, continued

Series C Mining	Superseded by E² Mining
KDCM3400L5MWS10	E2KM3400MLWS10
KDCM3400L5WD07	E2KM3400MLD07
KDCM3400MW	E2KM3400MW
KDCM3400N5MW	E2KM3400MNW
KDCM3400N5MWA06	E2KM3400MNWA06
KDCM3400N5WA02D07	E2KM3400MNA02D07
KDCM3400R5MW	E2KM3400MRW
KDCM3400W	E2KM3400W
KDCM3400W5MW	E2KM3400MWW
KDCMDMD07	E2KM3400MDD07
KDCMNA2D7	E2KM3400MNA02D07
KDM2400F	E2K2400F
KDM2400G5MS50	E2K2400MGWS50
KDM2400G5MW	E2K2400MGW
KDM2400W5MW	E2K2400MWW
KDM2400W5MWA06D07S10	E2K2400MWA06D07S10
KDM2400W5MWA06D10S10	E2K2400MWA06D10S10
KDM2400W5MWD07	E2K2400MWD07
KDM2400W5MWD07S10	E2K2400MWD07S10
KDM2400W5MWD10	E2K2400MWD10
KDM2400W5MWD10S10	E2K2400MWD10S10
KDM2400W5MWS10	E2K2400MWWS10
KDM3100W	E2K3100W
KDM3125W	E2K3125W
KDM3150W	E2K3150W
KDM3150WA06	E2K3150WA06
KDM3175W	E2K3175W
KDM3200W	E2K3200W
KDM3225A5W	E2K3225AW
KDM3225D5A13D09U18	E2K3225DA13D09U18
KDM3225D5MW	E2K3400MDW
KDM3225D5W	E2K3225DW
KDM3225F	E2K3400F
KDM3225W	E2K3225W
KDM3225WK37	E2KE3225W
KDM3225WK37U18	E2KE3225WU18
KDM3225WK38	E2KE3225MW
KDM3250W	E2K3250W
KDM3300W	E2K3300W
KDM3300WA06U18	E2K3300WA06U18
KDM3300WS10	E2K3300WS10
KDM3350W	E2K3350W
KDM3400D5MW	E2K3400MDW
KDM3400D5W	E2K3400DW
KDM3400D5WU18	E2K3400DWU18
KDM3400F	E2K3400F
KDM3400F5MW	E2K3400MFW
KDM3400FK37A06D09D18	E2KE3400A06D09D18
KDM3400G5A06D09U18	E2K3400GA06D09U18
KDM3400G5A13D09U18	E2K3400GA13D09U18
KDM3400G5MW	E2K3400MGW
KDM3400G5W	E2K3400GW
KDM3400G5WA06	E2K3400GWS10
KDM3400G5WS10	E2K3400GWS10
KDM3400G5WU18	E2K3400GWU18
KDM3400J5MW	E2K3400MJW
KDM3400K5MS54	E2K3400MKWS54
KDM3400K5MW	E2K3400MKW
KDM3400L5MW	E2K3400MLW
KDM3400MW	E2K3400MW
KDM3400MWA06U18	E2K3400MWA06U18
KDM3400N5MW	E2K3400MNW
KDM3400R5MW	E2K3400MRW
KDM3400W	E2K3400W
KDM3400W5MW	E2K3400MWW
KEM3100T	KEM3100T
KEM3125T	KEM3125T
KEM3150T	KEM3150T
KEM3150TM	KEM3150TM
KEM3200T	KEM3200T
KEM3225T	KEM3225T
KEM3225T2	KEM3225T2
KEM3225TM	KEM3225TM
KEM3225TM2	KEM3225TM2
KM2225TA5	E2K2225TA
KM2225TA5M	E2K2400TMA
KM2225TD5	E2K2225TD
KM2225TD5M	E2K2400TMD
KM2400TD5	E2K2400TD
KM2400TD5M	E2K2400TMD

E² Cross-Reference, continued

Series C Mining	Superseded by E² Mining
KM2400TG5M	E2K2400TMG
KM2400TN5M	E2K2400TMN
KM2400TW5M	E2K2400TMW
KM3100T	E2K3100T
KM3125T	E2K3125T
KM3150T	E2K3150T
KM3175T	E2K3175T
KM3200T	E2K3200T
KM3225T	E2K3225T
KM3225TA5	E2K3225TA
KM3225TA5M	E2K3400TMA
KM3225TD5	E2K3225TD
KM3225TD5M	E2K3400TMD
KM3250T	E2K3250T
KM3300T	E2K3300T
KM3350T	E2K3350T
KM3400T	E2K3400T
KM3400TD5	E2K3400TD
KM3400TF5M	E2K3400TMF
KM3400TG5M	E2K3400TMG
KM3400TJ5M	E2K3400TMJ
KM3400TK5M	E2K3400TMK
KM3400TL5M	E2K3400TML
KM3400TM	E2K3400TM
KM3400TN5M	E2K3400TMN
KM3400TR5M	E2K3400TMR
KM3400TW5M	E2K3400TMW
LDCM3600EMA05W	E2LEM3600MA05W
LDCM3600F	E2LM3600F
LDM3600F	E2L3600F

Series C Mining	Superseded by E² Mining
LEM3300T	LEM3300T
LEM3350T	LEM3350T
LEM3400T	LEM3400T
LEM3400T2	LEM3400T2
LEM3400TM	LEM3400TM
LEM3400TM2	LEM3400TM2
LEM3600T	LEM3600T
LEM3600TM	LEM3600TM
LM3600TL6M	E2L3600TML
LM3600TN6M	E2L3600TMN
LM3600TP6M	E2L3600TMP
LM3600TR6M	E2L3600TMR
LM3600TS6M	E2L3600TM
LM3600TX6M	E2L3600TMX
UVE3LP08K	UVE3LP08K
UVE4LP08K	UVE4LP08K

Additional Information on Mining Breakers

Source	Description
TD01217001E	E² Mining Circuit Breaker Dimensional Data
BR01217001E	E² Mining Circuit Breaker Brochure
TC01217001E	E² Mining Circuit Breaker Time Current Curves
www.eaton.com/mining	Mining and Metals

GFR Relay

Contents

Description	*Page*
Engine Generator Circuit Breakers	**V4-T2-343**
Direct Current Circuit Breakers	**V4-T2-349**
PVGard Solar Circuit Breakers—600 Vdc Per-Pole and 1000 Vdc Poles-in-Series	**V4-T2-363**
E^2 Mining Service Circuit Breakers	**V4-T2-372**
Classic Mining Breakers	**V4-T2-398**
Add-On Ground Fault Protection—Type GFR	
Product Selection	**V4-T2-413**
Accessories	**V4-T2-414**
Technical Data and Specifications	**V4-T2-414**

Add-On Ground Fault Protection—Type GFR

Product Description

A Type GFR ground fault protection system, when properly installed on a grounded electrical system, will sense phase-to-ground fault currents. When the level of fault current is in excess of the pre-selected current pickup and time delay settings, the GFR relay will initiate a trip action of a disconnect device, which will open the faulted circuit and clear the fault.

The GFR devices are UL Class I devices designed to protect electrical equipment against extensive damage from arcing ground faults.

A basic Type GFR ground fault protection system consists of a ground fault relay, a ground fault current sensor and a disconnect device equipped with a shunt trip device. This disconnect device can be a molded case circuit breaker, a power circuit breaker, a bolted pressure switch or other fusible disconnect device, suitable for application with UL Class I ground fault sensing and relaying equipment.

Note: Suitable for either surface or semi-flush mounting.

Standards and Certifications

Eaton's GFR ground fault relays, current sensors, test panels and accessory devices are UL listed by Underwriters Laboratories in accordance with their standard for ground fault sensing and relaying equipment, UL 1053, under File E48381.

Note: Relays are also listed with CSA under their file number 43357.

Listed

Product Selection

Each installation requires:

- One relay unit (select trip ampere as required)
- One current sensor (select configuration required)
- One circuit breaker or disconnect device with shunt trip, or a shunt trip attachment for mounting in existing breaker
- Test panel (optional)

GFR Relay

GFR Relay

GFR Relay Types	Ground Fault Pickup Amperes 1–12 Catalog Number ①	5–60 Catalog Number ①	100–1200 Catalog Number ①
For 120 Volt 50/60 Hz Control			
Electrical reset with zone interlocking	**GFR12EI**	**GFR60EI**	**GFR1200EI**
Electrical reset without zone interlocking	**GFR12E**	**GFR60E**	**GFR1200E**
Mechanical reset with zone interlocking	**GFR12MI**	**GFR60MI**	**GFR1200MI**
Mechanical reset without zone interlocking	**GFR12M**	**GFR60M**	**GFR1200M**
For 120 Vdc Control			
Electrical reset with zone interlocking	—	—	**GFR1200EID**
Electrical reset without zone interlocking	—	—	**GFR1200ED**
Mechanical reset with zone interlocking	—	—	**GFR1200MID**
Mechanical reset without zone interlocking	—	—	**GFR1200MD**

Typical Current Sensor

Current Sensor

Window Size in Inches (mm)	Catalog Number
Used with Relays Rated 1–12 Amperes	
5.50 (139.7) I.D.	**1283C45G01**
Used with Relays Rated 5–60 Amperes	
2.50 (63.5) I.D.	**179C768G01**
5.50 (139.7) I.D.	**1256C13G01**
7.81 x 11.00 (198.4 x 279.4) Rect. ②	**1257C88G04**
3.31 x 24.94 (84.1 x 760.5) Rect. ②	**1257C92G03**
Used with Relays Rated 100–1200 Amperes	
2.50 (63.5) I.D.	**179C768G02**
5.50 (139.7) I.D.	**1256C13G02**
8.25 (209.6). I.D.	**179C767G02**
7.81 x 11.00 (198.4 x 279.4) Rect. ②	**1257C88G03**
9.94 x 16.94 (252.5 x 430.3) Rect. ②	**1257C90G02**
9.94 x 23.94 (252.5 x 608.1) Rect. ②	**1257C91G02**
15.94 x 19.94 (404.9 x 506.4) Rect. ②	**1257C89G02**
3.31 x 24.94 (84.1 x 633.5) Rect. ②	**1257C92G04**
6.75 x 29.64 (171.5 x 752.9) Rect. ②	**1255C39G03**

Notes

① Suitable for either surface or semi-flush mounting.
② One end removable for installation.

Accessories

Options

Additional optional equipment can be added to the protection system to meet the requirements of the specifying engineer, including:

- Ground fault test panel
- Ground fault warning indicator relay
- Ground fault indicating ammeter

GFR relays are available with zone selective interlocking circuitry to interlock several relays within the same system. This allows the relay which detects a ground fault to instantly clear the fault by tripping the disconnect device. The relay simultaneously sends a signal to relay units "upstream" from the fault to time delay or to block their operation completely. Current sensors in various designs provide a range of "window" sizes to accommodate standard bus and cable arrangements.

Shunt trip attachments may be ordered for field mounting in Eaton's molded case circuit breakers, or may be ordered factory installed in the breaker.

Test Panel (120 Vac)

Used to test the ground fault system, to give an indication the relay has tripped the breaker, and to reset the relay after tripping. These functions may be separately mounted pilot devices.

Note: When a mechanically reset relay is used with a test panel, both the relay and test panel must be reset following either a simulated ground fault test or actual ground fault. Not UL listed.

Optional Test Panel

Control	Test	Catalog Number
120 Volt 50/60 Hz	120 Volt 50/60 Hz	**GFRTP**

Ground Fault Warning Indicator

This is an accessory item for use with GFR relays with interlocking circuitry. At approximately 30–50% of the relay pickup setting, the indicator switches separate 120 Vac control power to a lamp or relay, (not included) to give an indication of a ground fault. The indicator is rated 110/120 Vac 50/60 Hz for a maximum indicator load of 0.5 amperes.

Ground Fault Warning Indicator

Description	Catalog Number
Manual reset	**1234C67G01**
Self-resetting	**1234C67G02**

Indicating Ammeter

The optional indicating ammeter connects to the sensor terminals through a momentary contact pushbutton, and will indicate (in amperes) any ground fault current flowing through the sensor. Kit includes the ammeter and pushbutton.

Note: Not UL listed.

Ammeter Kit

GFR System Used with	Kit Catalog Number
1–12 ampere	**752B820G01**
5–60 ampere	**752B820G02**
100–1200 ampere	**752B820G03**

Shunt Trip Attachments

Use 120 Vac shunt trips.

Faceplate

Recommended when these relays are semi-flush mounted, to close the door cutout opening.

Face Plate

Description	Catalog Number
Faceplate	**752B410G01**

Technical Data and Specifications

Sensor

- 600 volt, 50/60 Hz maximum system voltage

Electrical Ratings

GFR Relay

- Ground fault detection ranges:
  - 1 to 12, 5 to 60 or 100 to 1200 amperes
- Output contacts:
  - 240 volt, 50/60 Hz: 3.0 amperes
  - 120 volt, 50/60 Hz: 6.0 amperes
  - 28 Vdc: 3.0 amperes
  - 125 Vdc: 0.5 amperes
- Control power requirements:
  - 120 volt, 50/60 Hz or 125 Vdc (optional)

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Handle Mechanisms—Series G

Product Overview

Handle mechanisms are used to operate molded case circuit breakers, molded case switches and motor circuit protectors. They are available in three basic configurations—Flange Mounted, Through-the-Door and Direct (Close-Coupled)—providing safe, dependable operation and ease of installation.

Through-the-Door

- High-Performance Rotary
- Universal Rotary

Direct (Close-Coupled)

- Universal Direct

Flange Mounted

- Flex Shaft™

Handle mechanisms are used on enclosed circuit breakers, control panels and motor control centers in many different applications. Eaton has a handle mechanism for virtually any need.

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	
Product Selection	**V4-T2-417**
Dimensions	**V4-T2-420**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

High-Performance Rotary Handle Mechanisms

Product Description

The high-performance rotary handle mechanism uses a simple, yet robust design to make installation and operation easy. The external handle's key functional components are all metallic, ensuring reliability. The metal-on-metal interface between the handle and shaft prevents contaminant buildup that could impede operation, while UV and chemical agent resistant materials protect the handle from heat and fading in direct sunlight, as well as chemicals that may be introduced in harsh environments.

In addition to its robust design features, the handle mechanism has stand-off support that allows for easy operation with a gloved hand. With a shallow profile, the handle can easily be used in applications where an internal or double door is required.

The high-performance external handle can accept padlocks or multi-hasp locks. The door is interlocked when padlocked and cannot be bypassed.

Features

- NEMA Type 1/3R/12 (IP54) and NEMA Type 4/4X (IP65) ratings
- Black/Blue or Red/Yellow external handle colors
- Three shaft lengths—6, 12 and 24 inches, which can be cut to size to match enclosure depth
- Conveniently packaged as kit containing handle, shaft and mechanism
- Replacement parts are available separately
- Metallic functional components ensure reliability
- Metal-on-metal interface between handle and shaft
- UV and chemical agent-resistant materials protect the handle
- Shallow profile
- Compatible with both Series C and Series G molded case circuit breakers and molded case switch platforms
- Same handle can be used on multiple frame sizes, reducing the number of parts needed
- Red and yellow handles to designate emergency disconnecting means
- All handle mechanisms can accept padlocks or multi-hasp locks for added flexibility
- Fast, easy installation (see video on website for step-by-step instructions)

Standards and Certifications

The mechanisms for EG, JG and LG breakers have an internal handle that can be operated independent of door position, and locked-out to meet one of the key NFPA requirements (NFPA® 79) and UL 508A disconnect requirements.

- NEMA 1/3R/12, IP54
- NEMA 4/4X, IP65

UL Listed

Product Selection

Handle Mechanisms for Series G Frames

Kits Only (Kit Includes Shaft, Mechanism and Handle)—EG-, JG- and LG-Frame

	Description	Rating Type NEMA	IP	EG-Frame Catalog Number	JG-Frame Catalog Number	LG-Frame Catalog Number
S01 Blue Handle	S01 blue handle, 6-inch shaft	1/3R/12	54	**EGHMVD06B0 / 68C6040G25**	**JGHMVD06B0 / 68C6041G13**	—
		4/4X	65	**EGHMVD06BX0 / 68C6040G28**	**JGHMVD06BX0 / 68C6041G16**	—
	S01 blue handle, 12-inch shaft	1/3R/12	54	**EGHMVD12B0 / 68C6040G26**	**JGHMVD12B0 / 68C6041G14**	—
		4/4X	65	**EGHMVD12BX0 / 68C6040G29**	**JGHMVD12BX0 / 68C6041G17**	—
	S01 blue handle, 24-inch shaft ①	1/3R/12	54	**EGHMVD24B0 / 68C6040G27**	**JGHMVD24B0 / 68C6041G15**	—
		4/4X	65	**EGHMVD24BX0 / 68C6040G30**	**JGHMVD24BX0 / 68C6041G18**	—
S01 Red Handle	S01 red handle, 6-inch shaft	1/3R/12	54	**EGHMVD06R0 / 68C6040G31**	**JGHMVD06R0 / 68C6041G19**	—
		4/4X	65	**EGHMVD06RX0 / 68C6040G34**	**JGHMVD06RX0 / 68C6041G22**	—
	S01 red handle, 12-inch shaft	1/3R/12	54	**EGHMVD12R0 / 68C6040G32**	**JGHMVD12R0 / 68C6041G20**	—
		4/4X	65	**EGHMVD12RX0 / 68C6040G35**	**JGHMVD12RX0 / 68C6041G23**	—
	S01 red handle, 24-inch shaft ①	1/3R/12	54	**EGHMVD24R0 / 68C6040G33**	**JGHMVD24R0 / 68C6041G21**	—
		4/4X	65	**EGHMVD24RX0 / 68C6040G36**	**JGHMVD24RX0 / 68C6041G24**	—
S2 Blue Handle	S2 blue handle, 6-inch shaft	1/3R/12	54	**EGHMVD06B / 68C6040G13**	**JGHMVD06B / 68C6041G01**	**LGHMVD06B / 68C6042G01**
		4/4X	65	**EGHMVD06BX / 68C6040G16**	**JGHMVD06BX / 68C6041G04**	**LGHMVD06BX / 68C6042G04**
	S2 blue handle, 12-inch shaft	1/3R/12	54	**EGHMVD12B / 68C6040G14**	**JGHMVD12B / 68C6041G02**	**LGHMVD12B / 68C6042G02**
		4/4X	65	**EGHMVD12BX / 68C6040G17**	**JGHMVD12BX / 68C6041G05**	**LGHMVD12BX / 68C6042G05**
	S2 blue handle, 24-inch shaft ①	1/3R/12	54	**EGHMVD24B / 68C6040G15**	**JGHMVD24B / 68C6041G03**	**LGHMVD24B / 68C6042G03**
		4/4X	65	**EGHMVD24BX / 68C6040G18**	**JGHMVD24BX / 68C6041G06**	**LGHMVD24BX / 68C6042G06**
S2 Red Handle	S2 red handle, 6-inch shaft	1/3R/12	54	**EGHMVD06R / 68C6040G19**	**JGHMVD06R / 68C6041G07**	**LGHMVD06R / 68C6042G07**
		4/4X	65	**EGHMVD06RX / 68C6040G22**	**JGHMVD06RX / 68C6041G10**	**LGHMVD06RX / 68C6042G10**
	S2 red handle, 12-inch shaft	1/3R/12	54	**EGHMVD12R / 68C6040G20**	**JGHMVD12R / 68C6041G08**	**LGHMVD12R / 68C6042G08**
		4/4X	65	**EGHMVD12RX / 68C6040G23**	**JGHMVD12RX / 68C6041G11**	**LGHMVD12RX / 68C6042G11**
	S2 red handle, 24-inch shaft ①	1/3R/12	54	**EGHMVD24R / 68C6040G21**	**JGHMVD24R / 68C6041G09**	**LGHMVD24R / 68C6042G09**
		4/4X	65	**EGHMVD24RX / 68C6040G24**	**JGHMVD24RX / 68C6041G12**	**LGHMVD24RX / 68C6042G12**

Notes

① 24-inch handle comes with support bracket.

Shaft guide (68C6048G49) is optional and can be used with any high-performance handle listed above for greater alignment tolerance.

Handle Mechanisms for Series G Frames

Kits Only (Kit Includes Shaft, Mechanism and Handle)—NG- and RG-Frame

	Description	Rating Type NEMA	IP	NG-Frame Catalog Number	RG-Frame Catalog Number
S3 Blue Handle	S3 blue handle, 10-inch shaft	1/3R/12	54	**NGHMVD08B / 68C6043G01**	—
		4/4X	65	**NGHMVD08BX / 68C6043G03**	—
S3 Red Handle	S3 red handle, 10-inch shaft	1/3R/12	54	**NGHMVD08R / 68C6043G02**	—
		4/4X	65	**NGHMVD08RX / 68C6043G04**	—
S4 Blue Handle	S4 blue handle, 10-inch shaft	1/3R/12	54	**NGHMVD08BT / 68C6043G05**	**RGHMVD08B / 68C6044G01**
		4/4X	65	**NGHMVD08BTX / 68C6043G07**	**RGHMVD08BX / 68C6044G03**
S4 Red Handle	S4 red handle, 10-inch shaft	1/3R/12	54	**NGHMVD08RT / 68C6043G06**	**RGHMVD08R / 68C6044G02**
		4/4X	65	**NGHMVD08RTX / 68C6043G08**	**RGHMVD08RX / 68C6044G04**

Note

Shaft guide (68C6048G49) is optional and can be used with any high-performance handle listed above for greater alignment tolerance.

Separate Components for Series G Frames

Series G Components—Shafts and Mechanisms

Frame	Shaft Width	Shaft Length 6-Inch	10-Inch	12-Inch	24-Inch ①	Mechanism Only
EG	8 mm	**66A6010G95**	—	**66A6010G96**	**66A6010G97**	**1498D66G17**
JG	8 mm	**66A6010G95**	—	**66A6010G96**	**66A6010G98**	**69D6025G17**
LG	8 mm	**66A6010G95**	—	**66A6010G96**	**66A6010G99**	**69D6051G30**
NG	12 mm	—	**66A6013H01**	—	—	**69D9101G30**
RG	12 mm	—	**66A6013H01**	—	—	**69D9101G31**

Series G Components—Handles Only

Frame	Rating Type NEMA	IP	Handles Only S01 Blue/Black	S01 Red/Yellow	S2 Blue/Black	S2 Red/Yellow	S3 Blue/Black	S3 Red/Yellow	S4 Blue/Black	S4 Red/Yellow
EG	1/3R/12	54	**68C6048G41**	**68C6048G42**	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	**68C6048G03**	**68C6048G04**	—	—	—	—
JG	1/3R/12	54	**68C6048G41**	**68C6048G42**	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	**68C6048G03**	**68C6048G04**	—	—	—	—
LG	1/3R/12	54	—	—	**68C6048G01**	**68C6048G02**	**68C6048G05**	**68C6048G06**	—	—
	4/4X	65	—	—	**68C6048G03**	**68C6048G04**	**68C6048G07**	**68C6048G08**	—	—
NG	1/3R/12	54	—	—	—	—	**68C6048G05**	**68C6048G06**	**68C6048G09**	**68C6048G10**
	4/4X	65	—	—	—	—	**68C6048G07**	**68C6048G08**	**68C6048G11**	**68C6048G12**
RG	1/3R/12	54	—	—	—	—	—	—	**68C6048G09**	**68C6048G10**
	4/4X	65	—	—	—	—	—	—	**68C6048G11**	**68C6048G12**

Series G Components—Optional Caps

As an alternative to blue or red, a black, replaceable cap is available.

			Catalog Number
S01	66A6032H01	Black handle cap	**HPHC0DGX**
S2	66A6032H02	Black handle cap	**HPHC2DGX**
S3	66A6032H03	Black handle cap	**HPHC3DGX**

Series G Replacement Hardware

This kit provides replacement parts for Series G high performance handle only.

	Catalog Number
High-performance handle replacement parts kit	**66A6029G01**

Notes

① 24-inch handle comes with support bracket.

Shaft guide (68C6048G49) is optional and can be used with any high-performance handle listed above for greater alignment tolerance.

Dimensions

Approximate Dimensions in mm (Inches)

2

High-Performance Rotary Handle Mechanisms

Handle Type	Front Operation Direction of Operation	Door Drilling
Type S01		
		
Type S2		
		
Type S3		
		
Type S4		
		

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary Product Selection	**V4-T2-422**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Universal Rotary

Product Description

Eaton's Universal Rotary is suitable for use with Type 1 or 12 enclosure types. All rotary handle mechanisms include a handle "lock off" to prevent turning the breaker ON while in the OFF position, and indicate ON/OFF/Tripped/Reset positions. The Universal Rotary has the added feature of international markings for ON (I) and OFF (O). The Universal Rotary is made of molded material.

The Universal Rotary mechanisms for EG-, JG- and LG-Frame MCCBs can be operated by hand with the door open or "locked off" to prevent operation with the door open.

Standards and Certifications

Universal Rotary is UL listed and meets CSA requirements. Universal Rotary also meets IEC 60947-1 and IEC 60947-2 for international compliance. Rotary UL File Number is E64983.

Listed

Features

Features Comparison of Series C Rotary and Universal Rotary Handle Mechanism

Rotary	Number of Poles	NEMA Enclosure Type 1	3R	12	4/4X ①	Handle Lock-Off ②	Handle Indication: ON/OFF TRIPPED/RESET	International Markings ON (I) OFF (O)	Handle Material	Available Handle Colors	Handle Rotation	Shaft Lengths (Inches)
Series C rotary	—	■	■	■	■	■	■	■	Metal	Black	45 deg.	6, 12, 16, 24
Universal rotary	—	■	—	■	—	■	■	■	Molded plastic	Yellow/Red/Black	90 deg.	6, 12, 24

Notes

① Type 4/4X application requires special handle. See "Ordering Information."

② All rotary handle mechanisms include a handle "Lock Off" to prevent turning the breaker ON while in the OFF position.

Product Selection

Universal Rotary

Universal Rotary Through-the-Door Handle Mechanisms

Handle Color	UL Rating	Shaft Length in Inches (mm)	Complete Catalog Number ①
EG-Frame			
Black	1, 12	6.00 (152.4)	**EHMVD06B**
		12.00 (304.8)	**EHMVD12B**
		24.00 (609.6)	**EHMVD24B**
Red	1, 12	6.00 (152.4)	**EHMVD06R**
		12.00 (304.8)	**EHMVD12R**
		24.00 (609.6)	**EHMVD24R**
JG-Frame			
Black	1, 12	6.00 (152.4)	**FJHMVD06B**
		12.00 (304.8)	**FJHMVD12B**
		24.00 (609.6)	**FJHMVD24B**
Red	1, 12	6.00 (152.4)	**FJHMVD06R**
		12.00 (304.8)	**FJHMVD12R**
		24.00 (609.6)	**FJHMVD24R**
LG-Frame			
Black	1, 12	6.00 (152.4)	**KLHMVD06B**
		12.00 (304.8)	**KLHMVD12B**
		24.00 (609.6)	**KLHMVD24B**
Red	1, 12	6.00 (152.4)	**KLHMVD06R**
		12.00 (304.8)	**KLHMVD12R**
		24.00 (609.6)	**KLHMVD24R**
NG-Frame			
Black	1	6.00 (152.4)	**HMVD5B**
RG-Frame			
Black	1	9.00 (228.6)	**HMVD6B**

Series G Rotary

Series G Rotary Ordering Information

Shaft Length Inches (mm)	Complete Catalog Number ②	Separate Catalog Number			Catalog Number	
		Standard Handle ③	Breaker Mechanism ④	Shaft ⑤	IEC IP65 ⑥⑦	IEC IP66 ⑥⑦
N-Frame (ND and NG)						
6.00 (152.4)	**HM5R06**	**6648C22G21**	**6648C23G08**	**4217B37G08**	**WHM5R06**	**WHM5R06X**
12.00 (304.8)	**HM5R12**	**6648C22G21**	**6648C23G08**	**4217B37G05**	**WHM5R12**	**WHM5R12X**
16.00 (406.4)	**HM5R16**	**6648C22G21**	**6648C23G08**	**4217B37G06**	**WHM5R16**	**WHM5R16X**
24.00 (609.6)	**HM5R24**	**6648C22G21**	**6648C23G08**	**4217B37G07**	**WHM5R24**	**WHM5R24X**

Notes

① Complete catalog number includes handle, mechanism, shaft and mounting hardware.
② Complete catalog number includes the standard handle, mechanism, shaft and support brace/bracket.
③ Handle is designed suitable for NEMA Types 1, 3R and 12 enclosures. Use style number **6648C22G03** for Type 4/4X handle or add **X** Suffix to complete catalog number. Handle is cast aluminum.
④ Breaker mechanism includes a shaft support bracket and its parts. Shaft is.50-inch (12.7 mm).
⑤ Longer shafts,16-inch (406.4 mm) and 24-inch (609.6 mm), include an adjustable support extension.
⑥ IEC handle mechanism supplied with metric thread mounting hardware.
⑦ Complete catalog number includes a handle, mechanism and shaft.

Handle Mechanisms

Contents

Description	Page
Handle Mechanisms—Series G	V4-T2-415
High-Performance Rotary Handle Mechanisms	V4-T2-416
Universal Rotary	V4-T2-421
Direct (Close-Coupled) Handle Mechanisms Flex Shaft	V4-T2-424
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	V4-T2-429
Series C Rotary	V4-T2-433
Universal Rotary	V4-T2-435
Direct (Close-Coupled) Handle Mechanisms	V4-T2-437
Flex Shaft	V4-T2-439
Handle Extension	V4-T2-442

Direct (Close-Coupled) Handle Mechanisms

Product Description

Direct (close-coupled) handle mechanisms mount directly to the circuit breaker. They are used in shallow enclosures where the standard variable depth Through-the-door type mechanism is not practical or cannot be used.

The Universal Direct handle mechanisms are rated Type 1 and Type 12.

The Universal Direct handle mechanism is available as standard with a door interlock to prevent opening the enclosure while the circuit breaker is in the ON position. It is also available without a door interlock.

Application Description

Direct (close-coupled) handle mechanisms are typically used for applications where high volume, standardized enclosures are being fabricated.

Standards and Certifications

The Universal Direct handle mechanism is UL listed, IEC 60947-1 and IEC 60947-2 compliant, and meets CSA requirements.

UL Listed

Product Selection

Universal Direct (EG–LG)

Universal Direct Handle Mechanisms

Frame	Black Handle Color With Interlock Catalog Number	Black Handle Color Without Interlock Catalog Number	Red Handle Color With Interlock Catalog Number	Red Handle Color Without Interlock Catalog Number
EG	EHMCCBI	EHMCCB	EHMCCRI	EHMCCR
JG	JHMCCBI	JHMCCB	JHMCCRI	JHMCCR
LG	LHMCCBI	LHMCCB	LHMCCRI	LHMCCR

Handle Mechanisms



Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	
Product Selection	**V4-T2-425**
Accessories	**V4-T2-426**
Dimensions	**V4-T2-426**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Flex Shaft

Product Description

Flange-Mounted Handle Mechanisms

Flange-mounted handle mechanisms mount on the flange of an enclosure door. The Flex Shaft is an extra heavy-duty mechanism that includes a flexible shaft in various lengths, 3 feet (0.9m) through 10 feet (3m) for use with various size enclosures.

The Flex Shaft handle will accept up to three padlock shackles, each with a maximum diameter of 3/8 inches (9.5 mm). It can be used with Type12 fabricated enclosures. An optional handle is available for Flex Shaft that is suitable for use with Type 4 environments.

Flex Shaft comes preset from the factory, requiring only minor field adjustments on installation, which takes about 10 minutes—a significant time savings compared to installation of other types of flange handle mechanisms. The Flex Shaft mechanism also takes up less interior enclosure space than competitive designs, and the handle fits standard flange cutouts. Flex Shaft handle can be remotely mounted from breaker, where an operator can use it by "funneling" the cable through conduit.

Standards and Certifications

Flex Shaft is UL listed under File E64983 and meets CSA requirements.

Listed

Product Selection

Note: Type 4X handle mechanisms are available. Add Suffix X to the complete Catalog Number.

Note: When selecting the length of shaft, ensure minimum bending radius of 4 inches (101.6 mm) is maintained to operate properly.

Note: The standard method of shipment includes the mechanism preset at the factory; however, minor field adjustments may be required.

Flex Shaft

Flex Shaft Flange-Mounted Handle Mechanisms ①②

Breaker Frame	Flexible Shaft Length in Feet (m) 2 (0.6) Catalog Number	3 (0.9) Catalog Number	4 (1.2) Catalog Number	5 (1.3) Catalog Number	6 (1.8) Catalog Number
EG	EHMFS02	EHMFS03	EHMFS04	EHMFS05	EHMFS06
JG	N/A	JHMFS03	JHMFS04	JHMFS05	JHMFS06
LG	N/A	—	LHMFS04	—	—
NG	N/A	N/A	F5S04C	F5S05C	F5S06C
RG	N/A	N/A	F6S04	F6S05	F6S06

Breaker Frame	Flexible Shaft Length in Feet (m) 7 (2.1) Catalog Number	8 (2.4) Catalog Number	9 (2.7) Catalog Number	10 (3.1) Catalog Number
EG	EHMFS07	EHMFS08	EHMFS09	EHMFS10
JG	JHMFS07	JHMFS08	JHMFS09	JHMFS10
LG	LHMFS07	—	—	LHMFS10
NG	N/A	N/A	N/A	F5S10C
RG	N/A	N/A	N/A	N/A

High-Performance Flex Shaft

High-Performance Flex Shaft Flange Mounted Handle Mechanism ①②

Breaker Frame	Flexible Shaft Length in Feet (m) 2 (0.6) Catalog Number	3 (0.9) Catalog Number	4 (1.2) Catalog Number	5 (1.3) Catalog Number	6 (1.8) Catalog Number
EG	EGFS02HP	EGFS03HP	EGFS04HP	EGFS05HP	EGFS06HP
JG	N/A	JGFS03HP	JGFS04HP	JGFS05HP	JGFS06HP
LG	N/A	N/A	LGFS04HP	N/A	N/A
NG	N/A	N/A	F5S04HP	F5S05HP	F5S06HP
RG	N/A	N/A	F6S04HP	F6S05HP	F6S06HP

Breaker Frame	Flexible Shaft Length in Feet (m) 7 (2.1) Catalog Number	8 (2.4) Catalog Number	9 (2.7) Catalog Number	10 (3.1) Catalog Number
EG	EGFS07HP	EGFS08HP	EGFS09HP	EGFS10HP
JG	JGFS07HP	JGFS08HP	JGFS09HP	JGFS10HP
LG	LGFS07HP	N/A	N/A	LGFS10HP
NG	N/A	N/A	N/A	F5S10HP
RG	N/A	N/A	N/A	N/A

Notes

① Three-pole only for EG-; three- and four-pole for JG- and LG-Frame.

② EG-, JG- and LG-Frame can be left- or right-hand mounted.

Accessories

Handle Auxiliary Switch—Early Break Design, 1A–1B Contact for Flex Shaft

Breaker Frame	Catalog Number
EG	**AUX1EBFSEG**
JG	**AUX1EBFSJG**
LG	**AUX1EBFSLG**

Auxiliary contact changes state prior to parting of breaker contacts to allow for shutdown of equipment. Contacts mounted on breaker mechanism customer supplied wiring.

Type 12 Safety Door Hardware for Flex Shaft (E- through R-Frame) ①

Catalog Number ②
C361KJ4
C361KJ6
C361KR

Dimensions

Type 12 Safety Door Hardware for Flex Shaft (E- through R-Frame) ①

Catalog Number ②	Handle Length in Inches (mm)
C361KJ4	4.00 (101.6)
C361KJ6	6.00 (152.4)
C361KR	Roller latch ③

Notes

① Customer: Consult with box manufacturer for correct door hardware and any adapters required for assembly.

② The 1/4-inch x 1/2-inch (6.35 x 12.7 mm) standard mill rectangular locking bar is not supplied with these kits.

③ Third roller latch for use with 4.00- or 6.00-inch (101.6 or 152.4 mm) handle when three-point latching is required.

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Handle Mechanisms—Series C

Product Overview

Handle mechanisms are used to operate molded case circuit breakers, molded case switches and motor circuit protectors. They are available in three basic configurations—Flange Mounted, Through-the-Door and Direct (Close-Coupled)—providing safe, dependable operation and ease of installation.

Through-the-Door

- High-Performance Rotary
- Series C Rotary
- Universal Rotary

Direct (Close-Coupled)

- Universal Direct
- Euro IEC
- G Direct

Flange Mounted

- Flex Shaft
- C371

Handle mechanisms are used on enclosed circuit breakers, control panels and motor control centers in many different applications. Eaton has a handle mechanism for virtually any need.

Through-the-Door Handle Mechanisms

Eaton's through-the-door handle mechanisms mount on the front of an enclosure or cabinet door and externally operate the circuit breaker via a variable depth shaft or a linear operator (Type MC). Each rotary type handle mechanism includes a handle, base operating mechanism and shaft that can be cut to various lengths.

Series C Rotary and Universal Rotary handle mechanisms are for use with molded case circuit breakers (G, F, J, K, L, MDL), molded case switches and motor circuit protectors.

Type 4/4X handles are similar to standard handles except they include an internal neoprene gasket. Type 4/4X handle style number is 6648C22G03. Due to gasketing effect between the handle and the housing, the handle may not indicate a tripped position.

Universal Rotary F-Frame

Direct (Close-Coupled) Handle Mechanisms

Direct (close-coupled) handle mechanisms mount directly to the circuit breaker. They are used in shallow enclosures where the standard variable depth Through-the-door type mechanism is not practical or cannot be used. They are typically for applications where high volume, standardized enclosures are being fabricated.

The Euro IEC Direct handle mechanism can be used on F- through R-Frames.

The G Direct is available with a black or the yellow handle, and with or without a shroud. It is suitable for use with NEMA 1 enclosures. It is for use only with the G-Frame (GD, GC, GHC, GMCP).

An escutcheon ring and interlock clip are provided as standard. The standard design includes a lock-off feature.

Flange-Mounted Handle Mechanisms

Flange-mounted handle mechanisms mount on the flange of an enclosure door. The Flex Shaft is an extra heavy-duty mechanism that includes a flexible shaft in various lengths, 3 feet (0.9m) through 10 feet (3m) for use with various size enclosures.

The Flex Shaft handle will accept up to three padlock shackles, each with a maximum diameter of 3/8-inch (9.5 mm). Can be used with NEMA 1, 3R and 12 fabricated enclosures. An optional handle is available for Flex Shaft that is suitable for use with NEMA 4 and 4X environments. Flex Shaft comes preset from the factory, requiring only minor field adjustments on installation, which takes about 10 minutes—a significant time savings compared to installation of other types of flange handle mechanisms. The Flex Shaft mechanism also takes up less interior enclosure space than competitive designs and the handle fits standard flange cutouts. Flex Shaft handle can be remotely mounted from breaker, where an operator can use it by "funneling" the cable through conduit.

The Type C371 circuit breaker operating mechanisms are designed for installation in control enclosures where main or branch circuit protective devices are required. All circuit breaker mechanisms are suitable for right-hand mounting.

Auxiliary contacts are not available for mounting on operating mechanisms. Where required, have them installed in circuit breaker.

Handle Extension

Handle extension is not included with J, K, L, M and N-Frame breakers. It must be purchased separately.

Standards and Certifications

Type C371 is UL Listed under File E62635.

Flex Shaft is UL Listed under File E64983 and meets CSA requirements.

Series C Rotary and Universal Rotary, are UL Listed and meet CSA requirements. Universal Rotary also meets IEC 60947-1 and IEC 60947-2 for international compliance. Rotary UL File Number is E64983.

The Universal Direct handle mechanism is UL 489 Listed, IEC 60947-1 and IEC 60947-2, and meets CSA requirements. The Euro IEC Direct handle mechanism is IEC-240-1. G Direct is UL Listed and meets CSA requirements.

Listed

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Product Selection	**V4-T2-430**
Dimensions	**V4-T2-432**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

High-Performance Rotary Handle Mechanisms

Product Description

The high-performance rotary handle mechanism uses a simple, yet robust design to make installation and operation easy. The external handle's key functional components are all metallic, ensuring reliability. The metal-on-metal interface between the handle and shaft prevents contaminant buildup that could impede operation, while UV and chemical agent resistant materials protect the handle from heat and fading in direct sunlight, as well as chemicals that may be introduced in harsh environments.

In addition to its robust design features, the handle mechanism has stand-off support that allows for easy operation with a gloved hand. With a shallow profile, the handle can easily be used in applications where an internal or double door is required.

The high-performance external handle can accept padlocks or multi-hasp locks. The door is interlocked when padlocked and cannot be bypassed.

Features

- NEMA Type 1/3R/12 (IP54) and NEMA Type 4/4X (IP65) ratings
- Black/Blue or Red/Yellow external handle colors
- Three shaft lengths—6, 12 and 24 inches, which can be cut to size to match enclosure depth
- Conveniently packaged as kit containing handle, shaft and mechanism
- Replacement parts are available separately
- Metallic functional components ensure reliability
- Metal-on-metal interface between handle and shaft
- UV and chemical agent-resistant materials protect the handle
- Shallow profile
- Compatible with both Series C and Series G molded case circuit breakers and molded case switch platforms
- Same handle can be used on multiple frames sizes reducing the number of parts needed
- Red and yellow handles to designate emergency disconnecting means
- All handle mechanisms can accept padlocks or multi-hasp locks for added flexibility
- Fast, easy installation (see video on website for step-by-step instructions)

Standards and Certifications

The mechanisms for EG, JG and LG breakers have an internal handle that can be operated independent of door position, and locked-out to meet one of the key NFPA requirements (NFPA® 79) and UL 508A disconnect requirements.

- NEMA 1/3R/12, IP54
- NEMA 4/4X, IP65

UL Listed

Product Selection

Handle Mechanisms for Series C Frames

Kits Only (Kit Includes Shaft, Mechanism and Handle)—GC/GD- and GMCP-Frame

	Description	Rating Type NEMA	IP	GC/GD-Frame Catalog Number	GMCP-Frame Catalog Number
S01 Blue Handle	S01 blue handle, 12-inch shaft	1/3R/12	54	**GCHMVD12B / 68C6039G01**	**GMHMVD12B / 68C6039G05**
		4/4X	65	**GCHMVD12BX / 68C6039G03**	**GMHMVD12BX / 68C6039G07**
S01 Red Handle	S01 red handle, 12-inch shaft	1/3R/12	54	**GCHMVD12R / 68C6039G02**	**GMHMVD12R / 68C6039G06**
		4/4X	65	**GCHMVD12RX / 68C6039G04**	**GMHMVD12RX / 68C6039G08**

Separate Components for Series C Frames

Series C Components—Shaft and Mechanism

Frame	Shaft Width	Shaft Length 6-Inch	10-Inch	12-Inch	Mechanism Only
GC/GD	6 mm	—	—	**66A6013H02**	**GCHMVD / 2A92095G15**
GMCP	6 mm	—	—	**66A6013H02**	**GMHMVD / 2A92095G16**
GD	8 mm	**66A6010G95**	—	**66A6010G96**	**1498D34G90**
FD	8 mm	**66A6010G95**	—	**66A6010G96**	**1498D34G91**
JD	10 mm	**66A6012G15**	—	**66A6012G16**	**1498D34G92**
KD	10 mm	**66A6012G15**	—	**66A6012G16**	**1498D34G93**
LD	10 mm	**66A6012G15**	—	**66A6012G16**	**1498D34G94**
MDL	10 mm	**66A6012G15**	—	**66A6012G16**	**1498D34G95**
ND	12 mm	—	**66A6013H01**	—	**69D9101G30**
RD	12 mm	—	**66A6013H01**	—	**69D9101G31**

Note

Shaft guide (68C6048G49) is optional and can be used with any high-performance handle listed above for greater alignment tolerance.

Series C Components—Handles Only

Frame	Rating Type NEMA	IP	Handles Only S01 Blue/Black	S01 Red/Yellow	S2 Blue/Black	S2 Red/Yellow	S3 Blue/Black	S3 Red/Yellow	S4 Blue/Black	S4 Red/Yellow
GC/GD	1/3R/12	54	**68C6048G41**	**68C6048G42**	—	—	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	—	—	—	—	—	—
GMCP	1/3R/12	54	**68C6048G41**	**68C6048G42**	—	—	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	—	—	—	—	—	—
GD	1/3R/12	54	**68C6048G41**	**68C6048G42**	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	**68C6048G03**	**68C6048G04**	—	—	—	—
FD	1/3R/12	54	**68C6048G41**	**68C6048G42**	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	**68C6048G43**	**68C6048G44**	**68C6048G03**	**68C6048G04**	—	—	—	—
JD	1/3R/12	54	—	—	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	—	—	**68C6048G03**	**68C6048G04**	—	—	—	—
KD	1/3R/12	54	—	—	**68C6048G01**	**68C6048G02**	—	—	—	—
	4/4X	65	—	—	**68C6048G03**	**68C6048G04**	—	—	—	—
LD	1/3R/12	54	—	—	**68C6048G01**	**68C6048G02**	**68C6048G05**	**68C6048G06**	—	—
	4/4X	65	—	—	**68C6048G03**	**68C6048G04**	**68C6048G07**	**68C6048G08**	—	—
MDL	1/3R/12	54	—	—	**68C6048G01**	**68C6048G02**	**68C6048G05**	**68C6048G06**	—	—
	4/4X	65	—	—	**68C6048G03**	**68C6048G04**	**68C6048G07**	**68C6048G08**	—	—
ND	1/3R/12	54	—	—	—	—	**68C6048G05**	**68C6048G06**	**68C6048G09**	**68C6048G10**
	4/4X	65	—	—	—	—	**68C6048G07**	**68C6048G08**	**68C6048G11**	**68C6048G12**
RD	1/3R/12	54	—	—	—	—	—	—	**68C6048G09**	**68C6048G10**
	4/4X	65	—	—	—	—	—	—	**68C6048G11**	**68C6048G12**

Note

Shaft guide (68C6048G49) is optional and can be used with any high-performance handle listed above for greater alignment tolerance.

Dimensions

Approximate Dimensions in mm (Inches)

2

High-Performance Rotary Handle Mechanisms

Handle Type	Front Operation Direction of Operation	Door Drilling
Type S01		
		
Type S2		
		
Type S3		
		
Type S4		
		

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms. Universal Rotary	**V4-T2-416**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms.	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Product Selection	**V4-T2-434**
Universal Rotary	**V4-T2-435**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Series C Rotary

Product Description

Eaton's through-the-door handle mechanisms mount on the front of an enclosure or a cabinet door and externally operate the circuit breaker via a variable depth shaft or a linear operator (Type MC). Each rotary type handle mechanism includes a handle, a base operating mechanism and a shaft that can be cut to various lengths.

Series C Rotary handle mechanisms are used with molded case circuit breakers (F, J, K, L, MDL), molded case switches and motor circuit protectors.

These rotary handles are robust and durable, made entirely of metal parts. It also has a lock-out tag-out level at the tip of the handle for padlocking.

NEMA Type 4/4X handles are similar to standard handles except they include an internal neoprene gasket. NEMA Type 4/4X handle style number is 6648C22G03. Due to gasketing effect between the handle and the housing, the handle may not indicate a tripped position.

Standards and Certifications

Series C Rotary is UL listed and meets CSA requirements.

Listed

Features

Features Comparison of Series C Rotary and Universal Rotary Handle Mechanism

Rotary	Number of Poles	NEMA Enclosure Type 1	3R	12	4/4X ①	Handle Lock-Off ②	Handle Indication: ON/OFF TRIPPED/RESET	International Markings ON (I) OFF (O)	Handle Material	Available Handle Colors	Handle Rotation	Shaft Lengths (Inches)
Series C rotary	—	■	■	■	■	■	■	■	Metal	Black	45 deg.	6, 12, 16, 24
Universal rotary	—	■	—	■	—	■	■	■	Molded plastic	Yellow/Red/Black	90 deg.	6, 12, 24

Notes

① Type 4/4X application requires special handle. See "Ordering Information."

② All rotary handle mechanisms include a handle "Lock Off" to prevent turning the breaker ON while in the OFF position.

Product Selection

2

Through-the-Door Handle Mechanisms

Series C Rotary

Series C Rotary Ordering Information

Shaft Length Inches (mm)	Complete Catalog Number ①	Separate Catalog Number			Catalog Number	
		Standard Handle ②	Breaker Mechanism ③	Shaft ④	IEC IP65 ⑤⑥	IEC IP66 ⑤⑥
F-Frame						
6.00 (152.4)	**HM1R06**	**6648C22G25**	**6648C23G11**	**4217B37G08**	**WHM1R06**	**WHM1R06X**
12.00 (304.8)	**HM1R12**	**6648C22G25**	**6648C23G11**	**4217B37G05**	**WHM1R12**	**WHM1R12X**
16.00 (406.4)	**HM1R16**	**6648C22G25**	**6648C23G11**	**4217B37G06**	**WHM1R16**	**WHM1R16X**
24.00 (609.6)	**HM1R24**	**6648C22G25**	**6648C23G11**	**4217B37G07**	**WHM1R24**	**WHM1R24X**
J-Frame						
6.00 (152.4)	**HM2R06**	**6648C22G01**	**6648C23G21**	**4217B37G08**	**WHM2R06**	**WHM2R06X**
12.00 (304.8)	**HM2R12**	**6648C22G01**	**6648C23G21**	**4217B37G05**	**WHM2R12**	**WHM2R12X**
16.00 (406.4)	**HM2R16**	**6648C22G01**	**6648C23G21**	**4217B37G06**	**WHM2R16**	**WHM2R16X**
24.00 (609.6)	**HM2R24**	**6648C22G01**	**6648C23G21**	**4217B37G07**	**WHM2R24**	**WHM2R24X**
K-Frame						
6.00 (152.4)	**HM3R06**	**6648C22G01**	**6648C23G25**	**4217B37G08**	**WHM3R06**	**WHM3R06X**
12.00 (304.8)	**HM3R12**	**6648C22G01**	**6648C23G25**	**4217B37G05**	**WHM3R12**	**WHM3R12X**
16.00 (406.4)	**HM3R16**	**6648C22G01**	**6648C23G25**	**4217B37G06**	**WHM3R16**	**WHM3R16X**
24.00 (609.6)	**HM3R24**	**6648C22G01**	**6648C23G25**	**4217B37G07**	**WHM3R24**	**WHM3R24X**
L- and MDL-Frame						
6.00 (152.4)	**HM4R06**	**6648C22G11**	**6648C23G19**	**4217B37G08**	**WHM4R06**	**WHM4R06X**
12.00 (304.8)	**HM4R12**	**6648C22G11**	**6648C23G19**	**4217B37G05**	**WHM4R12**	**WHM4R12X**
16.00 (406.4)	**HM4R16**	**6648C22G11**	**6648C23G19**	**4217B37G06**	**WHM4R16**	**WHM4R16X**
24.00 (609.6)	**HM4R24**	**6648C22G11**	**6648C23G19**	**4217B37G07**	**WHM4R24**	**WHM4R24X**
MD/MDS						
6.00 (152.4)	**HM7R06**	**6648C22G21**	**6648C23G17**	**4217B37G08**	—	—
12.00 (304.8)	**HM7R12**	**6648C22G21**	**6648C23G17**	**4217B37G05**	—	—
16.00 (406.4)	**HM7R16**	**6648C22G21**	**6648C23G17**	**4217B37G06**	—	—
24.00 (609.6)	**HM7R24**	**6648C22G21**	**6648C23G17**	**4217B37G07**	—	—
N-Frame (ND and NG)						
6.00 (152.4)	**HM5R06**	**6648C22G21**	**6648C23G08**	**4217B37G08**	**WHM5R06**	**WHM5R06X**
12.00 (304.8)	**HM5R12**	**6648C22G21**	**6648C23G08**	**4217B37G05**	**WHM5R12**	**WHM5R12X**
16.00 (406.4)	**HM5R16**	**6648C22G21**	**6648C23G08**	**4217B37G06**	**WHM5R16**	**WHM5R16X**
24.00 (609.6)	**HM5R24**	**6648C22G21**	**6648C23G08**	**4217B37G07**	**WHM5R24**	**WHM5R24X**

Notes

① Complete catalog number includes the standard handle, mechanism, shaft and support brace/bracket.

② Handle is designed suitable for NEMA Types 1, 3R and 12 enclosures. Use style number **6648C22G03** for Type 4/4X handle or add **X** Suffix to complete catalog number. Handle is cast aluminum.

③ Breaker mechanism includes a shaft support bracket and its parts. Shaft is.50-inch (12.7 mm).

④ Longer shafts,16-inch (406.4 mm) and 24-inch (609.6 mm), include an adjustable support extension.

⑤ IEC handle mechanism supplied with metric thread mounting hardware.

⑥ Complete catalog number includes a handle, mechanism and shaft.

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	
Product Selection	**V4-T2-422**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Universal Rotary	**V4-T2-435**
Product Selection	**V4-T2-436**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Universal Rotary

Product Description

Eaton's Universal Rotary is suitable for use with Type 1 or 12 enclosure types. All rotary handle mechanisms include a handle "lock off" to prevent turning the breaker ON while in the OFF position, and indicate ON/OFF/Tripped/Reset positions. The Universal Rotary has the added feature of international markings for ON (I) and OFF (O). The Universal Rotary is made of molded material.

The Universal Rotary mechanisms for EG-, JG- and LG-Frame MCCBs can be operated by hand with the door open or "locked off" to prevent operation with the door open.

Standards and Certifications

Universal Rotary is UL listed and meets CSA requirements. Universal Rotary also meets IEC 60947-1 and IEC 60947-2 for international compliance. Rotary UL File Number is E64983.

Listed

Features

Features Comparison of Series C Rotary and Universal Rotary Handle Mechanism

Rotary	Number of Poles	NEMA Enclosure Type 1	3R	12	4/4X ①	Handle Lock-Off ②	Handle Indication: ON/OFF TRIPPED/RESET	International Markings ON (I) OFF (O)	Handle Material	Available Handle Colors	Handle Rotation	Shaft Lengths (Inches)
Series C rotary	—	■	■	■	■	■	■	■	Metal	Black	45 deg.	6, 12, 16, 24
Universal rotary	—	■	—	■	—	■	■	■	Molded plastic	Yellow/Red/Black	90 deg.	6, 12, 24

Notes

① Type 4/4X application requires special handle. See "Ordering Information."

② All rotary handle mechanisms include a handle "Lock Off" to prevent turning the breaker ON while in the OFF position.

Product Selection

Universal Rotary F-Frame

Universal Rotary F-Frame

Series C Universal Rotary ①

Handle Color	Shaft Length in Inches (mm)	Complete Catalog Number
G-Frame		
Black	6.00 (152.4)	**GHMVD06B**
	12.00 (304.8)	**GHMVD12B**
Red	6.00 (152.4)	**GHMVD06R**
	12.00 (304.8)	**GHMVD12R**
F-Frame		
Black	6.00 (152.4)	**FHMVD06B**
	12.00 (304.8)	**FHMVD12B**
Red	6.00 (152.4)	**FHMVD06R**
	12.00 (304.8)	**FHMVD12R**
	24.00 (609.6)	**FHMVD24R**
J-Frame		
Black	6.00 (152.4)	**JHMVD06B**
	12.00 (304.8)	**JHMVD12B**
Red	6.00 (152.4)	**JHMVD06R**
	12.00 (304.8)	**JHMVD12R**
K-Frame		
Black	6.00 (152.4)	**KHMVD06B**
	12.00 (304.8)	**KHMVD12B**
Red	6.00 (152.4)	**KHMVD06R**
	12.00 (304.8)	**KHMVD12R**
L-Frame		
Black	6.00 (152.4)	**LHMVD06B**
	12.00 (304.8)	**LHMVD12B**
Red	6.00 (152.4)	**LHMVD06R**
	12.00 (304.8)	**LHMVD12R**

Note

① Only available as complete handle mechanism. Parts not sold separately.

Handle Mechanisms

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms Flex Shaft	**V4-T2-424**
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Product Selection	**V4-T2-438**
Flex Shaft	**V4-T2-439**
Handle Extension	**V4-T2-442**

Direct (Close-Coupled) Handle Mechanisms

Product Description

Direct (close-coupled) handle mechanisms mount directly to the circuit breaker. They are used in shallow enclosures where the standard variable depth Through-the-door type mechanism is not practical or cannot be used.

The Universal Direct handle mechanisms are rated Type 1 and Type 12.

The Universal Direct handle mechanism is available as standard with a door interlock to prevent opening the enclosure while the circuit breaker is in the ON position. It is also available without a door interlock.

Application Description

Direct (close-coupled) handle mechanisms are typically used for applications where high volume, standardized enclosures are being fabricated.

Standards and Certifications

The Universal Direct handle mechanism is IEC 60947-1 and IEC 60947-2 compliant.

Product Selection

Direct (Close-Coupled) Handle Mechanisms

Euro IEC Direct

Frame	Black Handle Catalog Number
F	**HMCC1B**
K	**HMCC3B**
L and M	**HMCC4B**
N	**HMVD5B**
R	**HMVD6B**

G Direct ①

Frame	Black Handle With Shroud Catalog Number	Without Shroud Catalog Number	Yellow Handle With Shroud Catalog Number	Without Shroud Catalog Number
GD/GHC	**HRGCC1S**	**HRGCC10**	**HRGCC3S**	**HRGCC30**
GMCP	**HRGMC1S**	**HRGMC10**	**HRGMC3S**	**HRGMC30**

Note

① Suitable for use on two- or three-pole G-Frame.

Handle Mechanisms



Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Product Selection	**V4-T2-440**
Handle Extension	**V4-T2-442**

Flex Shaft

Product Description

Flange-Mounted Handle Mechanisms

Flange-mounted handle mechanisms mount on the flange of an enclosure door. The Flex Shaft is an extra heavy-duty mechanism that includes a flexible shaft in various lengths, 3 feet (0.9m) through 10 feet (3m) for use with various size enclosures.

The Flex Shaft handle will accept up to three padlock shackles, each with a maximum diameter of 3/8 inches (9.5 mm). It can be used with Type12 fabricated enclosures. An optional handle is available for Flex Shaft that is suitable for use with Type 4 environments.

Flex Shaft comes preset from the factory, requiring only minor field adjustments on installation, which takes about 10 minutes—a significant time savings compared to installation of other types of flange handle mechanisms. The Flex Shaft mechanism also takes up less interior enclosure space than competitive designs, and the handle fits standard flange cutouts. Flex Shaft handle can be remotely mounted from breaker, where an operator can use it by "funneling" the cable through conduit.

Standards and Certifications

Flex Shaft is UL listed under File E64983 and meets CSA requirements.

Listed

Product Selection

2

Handle Mechanisms

Flex Shaft ①②

Breaker Frame	Flexible Shaft Length in Feet (m) 3 (0.9) Catalog Number	4 (1.2) Catalog Number	5 (1.5) Catalog Number	6 (1.8) Catalog Number	7 (2.1) Catalog Number	8 (2.4) Catalog Number	9 (2.7) Catalog Number	10 (3.0) Catalog Number
G ①	**F0S03C**	**F0S04C**	**F0S05C**	**F0S06C**	—	—	—	—
F	**F1S03C**	**F1S04C**	**F1S05C**	**F1S06C**	**F1S07C**	**F1S08C**	**F1S09C**	**F1S10C**
F (dual)	**F1S03CD**	**F1S04CD**	**F1S05CD**	**F1S06CD**	**F1S07CD**	**F1S08CD**	**F1S09CD**	**F1S10CD**
J	**F2S03C**	**F2S04C**	**F2S05C**	**F2S06C**	**F2S07C**	**F2S08C**	**F2S09C**	**F2S10C**
K	**F3S03C**	**F3S04C**	**F3S05C**	**F3S06C**	**F3S07C**	**F3S08C**	**F3S09C**	**F3S10C**
L and MDL	—	**F4S04C**	**F4S05C**	**F4S06C**	—	—	—	**F4S10C**
N	—	**F5S04C**	**F5S05C**	**F5S06C**	—	—	—	**F5S10C**
R	—	**F6S04**	**F6S05**	**F6S06**	—	—	—	—
MD, MDS (old)	—	**F7S04**	**F7S05**	**F7S06**	—	—	—	**F7S10C**

High Performance Flex Shaft ①②

Breaker Frame	Flexible Shaft Length in Feet (m) 3 (0.9) Catalog Number	4 (1.2) Catalog Number	5 (1.3) Catalog Number	6 (1.8) Catalog Number	7 (2.1) Catalog Number	8 (2.4) Catalog Number	9 (2.7) Catalog Number	10 (3.1) Catalog Number
G	**F0S03HP**	**F0S04HP**	**F0S05HP**	**F0S06HP**	**N/A**	**N/A**	**N/A**	**N/A**
F	**F1S03HP**	**F1S04HP**	**F1S05HP**	**F1S06HP**	**F1S07HP**	**F1S08HP**	**F1S09HP**	**F1S10HP**
F (dual)	**F1S03HPD**	**F1S04HPD**	**F1S05HPD**	**F1S06HPD**	**F1S07HPD**	**F1S08HPD**	**F1S09HPD**	**F1S10HPD**
J	**F2S03HP**	**F2S04HP**	**F2S05HP**	**F2S06HP**	**F2S07HP**	**F2S08HP**	**F2S09HP**	**F2S10HP**
K	**F3S03HP**	**F3S04HP**	**F3S05HP**	**F3S06HP**	**F3S07HP**	**F3S08HP**	**F3S09HP**	**F3S10HP**
L and MDL	**N/A**	**F4S04HP**	**F4S05HP**	**F4S06HP**	**N/A**	**N/A**	**N/A**	**F4S10HP**
N	**N/A**	**F5S04HP**	**F5S05HP**	**F5S06HP**	**N/A**	**N/A**	**N/A**	**F5S10HP**
R	**N/A**	**F6S04HP**	**F6S05HP**	**F6S06HP**	**N/A**	**N/A**	**N/A**	**N/A**

Flange-Mounted Handle Mechanisms

Type C371

Circuit Breaker or Motor Circuit Protector	Frame Size	Variable Depth Mounting Range Min./Max. ②③	Operating Mechanism Only ④ Catalog Number	Operating Mechanism w/ 4-Inch Handle For NEMA 1–12 Enclosure Catalog Number	Operating Mechanism w/ 4-Inch Handle For NEMA 4/4X Enclosure Catalog Number
HMCP and Series C—EHD, FDB, FD, FDC, HFD, ED	150	6.50–16 (165.1–406.4)	**C371E**	**C371E1**	**C371E2**
HMCP and Series C—HJD, JD, JDB, JDC	250	6.50–16.63 (165.1–422.4)	**C371F**	**C371F5**	**C371F6**
HMCP and Series C—DK, HKD, KD, KDB	400	6.50–16.63 (165.1–422.4)	**C371F**	**C371F5**	**C371F6**
Series C—HLD, LD, LDC	600	8.50–22 (215.9–558.8)	**C371G**	**C371G5**	**C371G6**
Series C MD, MDS—(No MDL)	800	8.75–22 (222.3–558.8)	**C371K**	**C371K5**	**C371K6**
Series C—HND, ND, NDC	1200	9.75–22 (247.7–558.8)	**C371K**	**C371K5**	**C371K6**

Notes

① Suitable for GC/GD MCCB; not suitable for GMCP.

② For increased maximum allowable depth, see connecting rods on **Page V4-T2-441**.

③ Dimensions shown are from panel flange surface.

④ Does not include handle.

Type 4/4X handle mechanisms are available. Add Suffix **X** to complete catalog number. Add Suffix I to complete catalog number for IEC handle. Original narrow handle design (No C Suffix) is available. Remove C from catalog number.

When selecting the length of shaft, ensure minimum bending radius of 4 inches (101.6 mm) (5 inches, 12.7 mm for L-, N- and R-Frames) is maintained to operate properly. The standard method of shipment includes the mechanism preset at the factory; however, minor field adjustments may be required.

Dual breakers operator available on F-Frame only. Only the F, J and K can mount LH and RH all other RH only.

Approximate Dimensions in Inches (mm)

Handle Only

Circuit Breaker Frame Size (Amperes)	NEMA Enclosure Type	Operating Handle Length	Catalog Number
150	1/3R/3/12	4.00 (101.6)	**C371H1**
	4/4X	4.00 (101.6)	**C371H2**
	1/3R/3/12	6.00 (152.4)	**C371H3**
	4/4X	6.00 (152.4)	**C371H4**
250–1200	1/3R/3/12	4.00 (101.6)	**C371H5**
	4/4X	4.00 (101.6)	**C371H6**
	1/3R/3/12	6.00 (152.4)	**C371H7**
	4/4X	6.00 (152.4)	**C371H8**

Channel Support Kit (Rod Not Supplied)

For use to prevent bending of the operating handle mounting surface. This is especially useful when the operating handle is mounted on a channel in a multi-door enclosure.

Amperes	Catalog Number
600–1200	**C371CS6**

Connecting Rods ①

Application	Catalog Number
Disconnect switches (30, 60, 100, 200 A sizes)	**C371CS1**
Circuit breakers (150, 250, 400 A sizes)	**C371CS1**
Circuit breakers (600, 800, 1200 A sizes)	**C371CS2**

Note

① Increase maximum allowable depth by 5 inches (127 mm).

Handle Extension

2

Contents

Description	*Page*
Handle Mechanisms—Series G	**V4-T2-415**
High-Performance Rotary Handle Mechanisms	**V4-T2-416**
Universal Rotary	**V4-T2-421**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-423**
Flex Shaft	
Handle Mechanisms—Series C	
High-Performance Rotary Handle Mechanisms	**V4-T2-429**
Series C Rotary	**V4-T2-433**
Direct (Close-Coupled) Handle Mechanisms	**V4-T2-437**
Flex Shaft	**V4-T2-439**
Product Selection	**V4-T2-440**
Handle Extension	**V4-T2-442**

Handle Extension

Product Description

- Suitable for use on two- or three-pole G-Frame
- Not included with J, K, L, M and N-Frame breakers; it must be purchased separately
- Included with R-Frame breakers

Product Selection

Handle Extension

Handle Extension ①②

Frame	Style Number
J, K	**HEX3**
L, M	**HEX4**
N	**HEX5**
R	**HEX6**

Notes

① Handle extension is not included with J, K, L, M and N-Frame breakers. It must be purchased separately.

② Handle extension is included with breaker with R-Frame breakers.

Power Breakers, Contactors and Fuses

Power Breakers, Contactors and Fuses Family

3.1 Power Circuit Breakers

Low Voltage Power Circuit Breakers V4-T3-2
Magnum DS Low Voltage Power Circuit Breakers V4-T3-6
Magnum MDSL Current Limiting Power Circuit Breaker V4-T3-12
Magnum SB Low Voltage Insulated Case Circuit Breakers V4-T3-15
Magnum IEC Rated Air Circuit Breakers V4-T3-23
Magnum DC (Direct Current) Low Voltage Switches V4-T3-33
Series NRX Low Voltage Power Circuit Breakers with PXR V4-T3-35
Series NRX Low Voltage Power Circuit Breakers with Digitrip V4-T3-47
Medium Voltage Circuit Breakers V4-T3-55

3.2 Medium Voltage Power Contactors

Product Overview V4-T3-72
SL MV Power Contactor 7.2 kV/160–400A V4-T3-74
SL MV Power Contactor 7.2 kV/800A V4-T3-83
SL MV Power Contactor 15 kV/300A V4-T3-87

3.3 Fuses General

Product Overview V4-T3-91
Power Fuse V4-T3-91
Power vs. Distribution V4-T3-91
Low vs. Medium vs. High Voltage V4-T3-91
Expulsion vs. Current Limiting (Definitions per ANSI C47.40-1993) . . . V4-T3-92
Fuse Types V4-T3-92
General Fuse Component Terms V4-T3-92

3.4 Expulsion Fuses

Product Description V4-T3-94
Accessories V4-T3-94
Catalog Number Selection V4-T3-95
Product Selection V4-T3-96

3.5 Current Limiting Fuses

Catalog Number Selection V4-T3-115
Product Selection V4-T3-117

3

Power Circuit Breaker

Contents

Description	*Page*
Low Voltage Power Circuit Breakers Features, Benefits and Functions	**V4-T3-3**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Low Voltage Power Circuit Breakers

Product Overview

Magnum Low Voltage Power Circuit Breakers for Global Application

Magnum® low voltage power circuit breakers enable comprehensive solutions to meet and exceed the unique and wide-ranging requirements of today's global power distribution systems. This powerful circuit breaker offering is designed for ultimate custom configuration and application flexibility, with the needs of the power distribution equipment user and the electrical equipment manufacturer in mind.

Four Product Families

Magnum consists of four product families; each provides specific ratings, features and approvals to optimize performance when applied in power distribution equipment and custom enclosures.

Magnum DS Low Voltage Power Circuit Breakers for ANSI Rated Switchgear Applications

- Up to 635 Vac
- 200 to 5000 A continuous
- 42 to 200 kA interrupting

Magnum DS Low Voltage Power Circuit Breaker Family ANSI Rated for Switchgear Applications

Magnum SB Low Voltage Insulated Case Circuit Breakers for Switchboard Applications

- Up to 635 Vac
- 200 to 5000 A continuous
- 50 to 150 kA interrupting

Magnum SB Low Voltage Insulated Case Circuit Breaker Family UL Rated for Switchboard Applications

Magnum IEC Air Circuit Breakers for IEC Rated Switchboards

- Up to 690 Vac
- 200 to 6300 A continuous
- 40 to 105 kA I_{cu}/I_{cs}

Magnum IEC Low Voltage Air Circuit Breaker Family

Magnum DC Switches for Direct Current Applications

- Up to 1000 Vdc
- 800 to 3200 A continuous
- 50 to 65 kA withstand rating

Magnum DC Switch Family

Features, Benefits and Functions

- **200 kA interruption ratings** with current limiting performance and low current let-through to reduce damaging energy to downstream equipment at high fault levels
- **Withstand ratings up to 100 kA** to maximize system coordination and selectivity
- **Four physical frame sizes** (Narrow, Standard, Double Narrow and Double) to promote breaker application in compact modular enclosures and improve enclosure density
- **Continuous current ratings from 800 to 6300A** with 100% rating at 104 °F (40 °C) and no derating on most ratings up to 122 °F (50 °C)
- **Fixed breaker mounting configurations** with horizontal and optional vertical and front connected terminal connections
- **Drawout breaker mounting configurations** with cassette and optional safety shutters
- **Three- and four-pole breaker configurations**
- **Through-the-door design** for human interface with the breaker compartment door closed
- **DC rated switches** for direct current applications
- **Two-step stored energy mechanism** for manually and electrical operated breakers
- **Digitrip™ RMS Trip Unit family protection** with four models each providing increasing levels of protection and feature options for coordination, information and diagnostics:
  - Microprocessor-based rms sensing
  - Basic to programmable overcurrent protection and alarms
  - Local display for information, status and diagnostics
  - Ampere, voltage and power metering
  - Power quality, harmonics and waveform capture
  - Communications with translators to common protocols
  - Zone selective interlocking for improved coordination
  - Integral Arcflash Reduction Maintenance System™
  - Breaker health monitoring
- **Field-installable accessories** (UL® listed) common across the breaker frames and designed to be easily installed in the field to service or modify the breaker at the point of use
- **Secondary terminal contacts** mounted at the top front of the breaker and away from the primary voltage areas for improved safety and access. Finger-safe terminal blocks accommodate ring-tongue or spade type terminals as standard
- **Arcflash Reduction Maintenance System** Eaton's patented Arcflash Reduction Maintenance System technology provides maintenance staff with improved safety of downstream maintenance locations using a simple and reliable method to reduce fault clearing times and energy during an arc flash event (radiation, sound, pressure, temperature). Arcflash Reduction Maintenance System uses a separate analog trip circuit, providing faster signal processing and interruption times than the standard (digital) "instantaneous" protection. The Arcflash Reduction Maintenance System function is activated either directly on the circuit breaker through a local switch or remotely through communications or a digital input

Through-the-Door Design for Human Interface with the Breaker Compartment Door Closed

High Technology Microprocessor-Based Digitrip RMS 1150+ Trip Units are Available With Advanced Features Like Programmable Overcurrent Settings, Power Metering, Power Quality and Communications

Breaker Features on Front Cover

The controls and indicators are functionally grouped on the breaker faceplate to optimize the human interface, visibility and ease of use. For maximum safety, a modern, through-the-door design permits access to the breaker levering system, trip unit, controls and indicators with the door closed.

① Red Mechanical Trip Flag Pop-out Indicator (Optional)—Interlocked Indicator Requiring Manual Reset is also Available

② Accessory Viewing Windows for:

- Shunt Trip Attachment (STA)
- Spring Release Device (SR)
- Undervoltage Release (UVR) Device or Second STA

③ Digitrip RMS Trip Unit (Model 520M Shown) Protected by Clear Cover

④ Contact Status Indicators:

- OPEN—Green
- CLOSED—Red

⑤ Spring Status Indicators:

- Charged—Yellow
- Discharged—White

⑥ Push OFF (Open) Pushbutton—Red

⑦ Push ON (Close) Pushbutton—Green

⑧ Manual Spring Charging Handle for Manually Charging the Stored Energy Springs

⑨ Mechanical Operations Counter (Optional)

⑩ Key Off Lock (Optional)

⑪ Padlockable Levering Device Shutter for Drawout Breakers

⑫ Color-Coded Position Indicator for Drawout Breakers:

- CONNECT—Red
- TEST—Yellow
- DISCONNECT—Green

Magnum DS Drawout Breaker



Accessory Viewing Windows Visibly Confirm the Breaker Shunt Trip, Spring Release, and UVR Installation and Their Control Voltage Rating

Through-the-Door Design for Human Interface with the Breaker Compartment Door Closed, for Example, Manually Charging the Stored Energy Springs

Drawout Breaker Levering Can be Accomplished With the Compartment Door Closed Without the Need for a Special Levering Tool

Breaker Internal Features

Magnum is designed for ease of access for inspection, modification and maintenance at the point of use. The breaker front cover is easily removed with four captive bolts, revealing the modular internal breaker features.

① Secondary Terminal Points for Internal Breaker Wiring Connections

② Breaker Accessory Mounting Deck with Three Positions for Mounting:

- Shunt Trip Attachment (STA)
- Spring Release Device (SR)
- Undervoltage Release (UVR) Device or Second STA

③ Digitrip RMS Trip Unit (Model 1150+ Shown)

④ Spring Charging Motor (Optional) for Electrically Charging the Stored Energy Springs

⑤ Manual Spring Charging Handle for Manually Charging the Stored Energy Springs

⑥ Padlockable Levering Device Shutter for Drawout Breakers

⑦ Color-Coded Position Indicator for Drawout Breakers:

- CONNECT—Red
- TEST—Yellow
- DISCONNECT—Green

⑧ Secondary Contact Blocks for Connection to External Cell Control Wiring

⑨ Removable Arc Chute Covers for Easy Access to Breaker Main Contacts

⑩ Primary Finger Cluster Disconnecting Contacts for Drawout Breaker are Mounted on the Breaker Element (Not in the Breaker Compartment) for Ease of Access for Inspection and Maintenance

Note: Some competitors mount the primary finger clusters inside the cell, requiring shutdown of the switchgear for inspection and maintenance.

⑪ Current Sensor Viewing Windows to View and Confirm Breaker Sensor Rating

⑫ Rigid Frame Housing (Thermoset Composite Resin) Providing Increased Strength and Durability



Magnum Drawout Breaker Front View With Front Cover Removed Showing Easy Access to the Breaker Internal Devices



Magnum Drawout Breaker Rear View Showing Primary Disconnecting Finger Clusters Mounted on the Breaker for Ease of Inspection

Magnum DS, MDSX and MDSL Circuit Breakers

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	
Catalog Number Selection	**V4-T3-7**
Technical Data and Specifications	**V4-T3-10**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Magnum DS Low Voltage Power Circuit Breakers

Product Description

Magnum DS is a true UL 1066 listed low voltage power circuit breaker family, designed for the highest performance requirements of switchgear and specialty enclosure applications.

- Magnum DS low voltage power circuit breakers have interruption ratings up to 200 kA at 480 Vac, and short-time withstand ratings up to 100 kA at 635 Vac with continuous current ratings up to 5000 A to maximize system coordination and selectivity
- Magnum MDSX current limiting power circuit breakers have 200 kA interruption ratings at 480 Vac with continuous current ratings up to 5000 A
- Magnum MDSL current limiting power circuit breakers have 200 kA interruption ratings at 600 Vac with continuous current ratings up to 2000 A

The Magnum MDSL current limiting power circuit breakers have integral current limiters to provide interruption ratings of 200 kA at 600 Vac.

The Magnum MDSX current limiting power circuit breakers have fast opening contacts to provide interruption ratings up to 200 kA at 480 Vac without fuses.

Standards and Certifications

UL and ANSI Test Certifications

Magnum DS meets or exceeds the applicable ANSI, NEMA®, UL and CSA® standards, including:

- ANSI C37.13 (Low Voltage AC Power Circuit Breakers Used in Enclosures)
- ANSI C37.16 (Preferred Ratings, Related Requirements, and Application Recommendations for Low Voltage Power Circuit Breakers and AC Power Circuit Breakers)
- ANSI C37.17 (Trip Devices for AC and General Purpose DC Low Voltage Power Circuit Breakers)
- ANSI C37.50 (Test Procedures for Low Voltage AC Power Circuit Breakers Used in Enclosures)
- UL 1066 (Standard for Low Voltage AC and DC Power Circuit Breakers Used in Enclosures)
- NEMA SG3 (This standard adopts ANSI C37.16 in its entirety)

Comprehensive Enclosure Solutions

Magnum DS has proven performance in Eaton manufactured switchgear with the following test certifications:

- UL 1558 (Certified Magnum DS Low Voltage Metal-Enclosed Switchgear)
- UL 1008 Standard for Transfer Switch Equipment
- UL, CSA 22.2.31 Low Voltage Assemblies

Approvals and Marks

- UL listed: Magnum DS Breaker UL File No. E52096 and Cassette UL File No. E204565
- ABS (American Bureau of Shipping) Type Listed Certificate Number 04-HS422844A-DUB
- Additional Magnum DS approvals and certificates can be found on www.eaton.com

Listed

Product Selection

Contact Eaton for pricing.

Catalog Number Selection

Magnum DS ANSI Breaker Product Family

MD S 4 12 3 V E A 06 MU

Breaker Type
MD = Magnum DS

Frame Type
S = Standard or double
N = Narrow or double narrow
D = MDDX only
E = High endurance

Interrupting/ Withstand Rating
4 = 42
5 = 50
6 = 65
8 = 85
C = 100
H = 130 (DSH)
E = 150 (DSE)
X = 200 (DSX/DDX)
L = 200 (DSL)

Continuous Amperes and Phasing (Facing Front of Breaker)
08 = 800 ABC
12 = 1200 ABC
16 = 1600 ABC
20 = 2000 ABC
25 = 2500 ABC
30 = 3000 ABC
32 = 3200 ABC or ABCABC
3N = 3200 AABBCC
4N = 4000 AABBCC
5N = 5000 AABBCC
40 = 4000 ABCABC
50 = 5000 ABCABC

Poles and Neutral (Facing Front of Breaker)
3 = Three
4 = Four (neutral left)

Mounting Configuration and Load Terminals
H = Fixed horizontal
V = Fixed vertical
L = Drawout (MDN)
W = Drawout (MDS)

Nameplate Language
E = English
A = Spanish

Current Limiter Selection
A = Non-DSL (no limiter)
D = MA250
E = MA300
F = MA400
G = MA600
H = MA800
K = MB1200
L = MB1600
M = MB2000
N = MD2500
P = MD3000

Sensor and Rating Plug Rating

NN = None	**13** = 1250
01 = 100	**16** = 1600
02 = 200	**20** = 2000
05 = 250	**25** = 2500
03 = 300	**30** = 3000
04 = 400	**32** = 3200
06 = 600	**40** = 4000
08 = 800	**50** = 5000
10 = 1000	
12 = 1200	

Trip Unit and Protection, and External Control Voltage When Required
NN = Non-automatic (no trip unit)
52 = 520 LSI
5G = 520 LSIG
M2 = 520M LSI
MT = 520M LSI (24/48 Vdc)
MU = 520M LSI (120 Vac)
MV = 520M LSI (240 Vac)
MQ = 520M LSI (125 Vdc)
MG = 520M LSIG
MH = 520M LSIG (24/48 Vdc)
MM = 520M LSIG (120 Vac)
MN = 520 LSIG (240 Vac)
MX = 520M LSIG (125 Vdc)
ME = 520M LSIA (24/48 Vdc)
MC = 520 LSIA (120 Vac)
MF = 520M LSIA (240 Vac)
MZ = 520M LSIA (125 Vdc)
CT = 520MC LSI (24/48 Vdc)
CU = 520MC LSI (120 Vac)
CV = 520MC LSI (240 Vac)
CQ = 520MC LSI (125 Vdc)
CH = 520MC LSIG (24/48 Vdc)
CM = 520MC LSIG (120 Vac)
CN = 520MC LSIG (240 Vac)
CX = 520MC LSIG (125 Vdc)
CE = 520MC LSIA (24/48 Vdc)
CC = 520MC LSIA (120 Vac)
CF = 520MC LSIA (240 Vac)
CY = 520MC LSIA (125 Vdc)
1A = 1150 LSI (24/48 Vdc)
1C = 1150 LSI (120 Vac)
1E = 1150 LSI (240 Vac)
1Q = 1150 LSI (125 Vdc)
1F = 1150 LSIG (24/48 Vdc)
1G = 1150 LSIG (120 Vac)
1H = 1150 LSIG (240 Vac)
1X = 1150 LSIG (125 Vdc)
1J = 1150 LSIA (24/48 Vdc)
1K = 1150 LSIA (120 Vac)
1M = 1150 LSIA (240 Vac)
1Y = 1150 LSIA (125 Vdc)

Magnum DS ANSI Breaker Product Family, continued

A W C H N E H K L A X

Shunt Trip (ST)
N = None
A = 110–127 Vac/Vdc
R = 208–240 Vac/Vdc
C = 24 Vdc
H = 48 Vdc
B = 110–127 Vac/Vdc (100% duty)
S = 220–250 Vac/Vdc (100% duty)
D = 24 Vdc (100% duty)
K = 48 Vdc (100% duty)
J = 60 Vdc (100% duty)
6 = 60 Vdc

Motor Operator
M = Manual operated
N = 110–125 Vac (5-sec)
W = 110–125 Vdc (5-sec)
T = 220–250 Vdc (5-sec)
P = 208–277 Vac (5-sec)
L = 24 Vdc (5-sec)
K = 48 Vdc (5-sec)
S = 60 Vdc (5-sec)
1 = 110–125 Vac (3-sec)
2 = 220–250 Vac (3-sec)
4 = 24 Vdc (3-sec)
8 = 48 Vdc (3-sec)
5 = 110–125 Vdc (3-sec)
9 = 220–250 Vdc (3-sec)

Spring Release Device (SRD)
N = None
A = 110–127 Vac/Vdc
R = 208–240 Vac/Vdc
C = 24 Vdc
H = 48 Vdc
S = 60 Vdc

Undervoltage Release (UVR) or 2nd Shunt Trip (ST)
N = None
A = UVR (110–127 Vac)
R = UVR (208–240 Vac)
C = UVR (24 Vdc)
H = UVR (48 Vdc)
D = UVR (60 Vdc)
E = UVR (110–125 Vdc)
F = UVR (220–250 Vdc)
G = UVR (32 Vdc)
X = UVR (380–415 Vac)
J = UVR (480 Vac)
K = UVR (600 Vac)
1 = 2nd ST (110–127 Vac/Vdc)
2 = 2nd ST (208–250 Vac/Vdc)
3 = 2nd ST (24 Vdc)
4 = 2nd ST (48 Vdc)
6 = 2nd ST (60 Vdc)
B = 2nd ST (110–127 Vac/Vdc 100% duty)
O = 2nd ST (220–250 Vac/Vdc 100% duty)
I = 2nd ST (24 Vdc 100% duty)
Q = 2nd ST (48 Vdc 100% duty)
9 = 2nd ST (60 Vdc 100% duty)

Auxiliary Switch
N = None
2 = 2A/2B
4 = 4A/4B
6 = 6A/6B

Bell Alarms Switch (OTS) with 2a/2b Contacts and/or Mechanical Trip Indicator

	Mech. Trip Indicator	Mech. Interlock for Manual Reset	OTS Switch with Two Form C Contacts
E =	No	—	No
N =	Yes	No	No
Y =	Yes	No	Yes
M =	Yes	Yes	No
L =	Yes	Yes	Yes
F =	Yes	No	Yes with 24 V reset
G =	Yes	No	Yes with 120 V reset
H =	Yes	No	Yes with 240 V reset
I =	Yes	Yes	Yes with 24 V reset
J =	Yes	Yes	Yes with 120 V reset
K =	Yes	Yes	Yes with 240 V reset

Padlock Provisions for Blocking Close and/or Open ACB Manual Pushbuttons
N = None
M = Metal (block close and open)
P = Plastic (block close and open)
C = Metal (block close only)
H = Plastic (block close only)
S = Metal swbd lock-off (block close, depress open)

Operations Counter and/or Keylock Provisions

	Counter	Keylock Provisions
N =	No counter	No locks
K =	No counter	Kirk lock
C =	No counter	Castell lock
R =	No counter	Ronis lock
S =	No counter	CES lock
A =	Counter	No lock
Y =	Counter	Kirk lock
L =	Counter	Castell lock
H =	Counter	Ronis lock indicator
E =	Counter	CES lock

Latch Check Switch/Trip Unit Metering Voltage Connection for Digitrip 1150 Trip Unit

	Latch Check Switch	1150 Voltage Connection
N =	None	Upper terminals
M =	None	Lower terminals
L =	LCS wired to SRD	Upper terminals
Y =	LCS Wired to SRD	Lower terminals
C =	LCS Wired External	Upper terminals
D =	LCS Wired External	Lower terminals

Breaker Shipping Options and Instructions
A = Fixed breaker alone with door kit
B = Fixed breaker alone with door kit and pre-wired
F = Fixed breaker alone without door kit
A = Drawout breaker alone without door frame kit
C = Drawout breaker in cassette (un-wired)
P = Drawout breaker in cassette (shutters)
S = Drawout breaker in cassette (shutters)
W = Drawout breaker in cassette (pre-wired and shutters)
Double frame drawout breakers ship without cassette drawout. ACBs ship in narrow and universal cassettes only.

Frame Use
X = All breakers

Cassette Magnum DS ANSI Breaker Product Family

M E 32 3 C A DN N NNN W C

Cassette Family
M = Standard or double frame
L = Narrow or double narrow frame

Interrupt Type
N = Cassettes (up to 100 kA)
L = MDSL cassettes (200 kA)
X = MDSX cassettes (200 kA)
D = MDDX cassettes (200 kA)

Continuous Amperes
16 = Up to 1600 A
20 = Up to 2000 A
32 = 2500 to 3200 A
40 = 1600 to 4000 A
50 = 2000 to 5000 A

Poles
3 = Three-pole
4 = Four-pole

Cassette Frame and Rear Terminals
P = Basic cassette (without vertical bus stabs)
C = Basic cassette with stabs (with vertical bus stab kit)
H = Narrow frame cassette (with horizontal terminal pads)
U = Universal cassette (with universal terminal pads)

Arc Hood
A = Arc hood installed
D = Dual baffled arc hood for ATS and DC applications ①

Door Frame and Gasket Kit
DN = Door frame and gasket kit included
XN = Door frame and gasket kit not included

Shutters
N = No shutters
S = Shutters installed

Future Use
NNN = All cassettes

Cassette Wiring
N = Un-wired
W = Cassette wired

Cassette Shipping
C = Cassette only
B = Breaker shipped in cassette

Note

① The arc hood option 'D' is recommended for use for ATS applications as well as on Magnum ANSI DC breakers, 'DAS' and 'DBS' configurations.

Technical Data and Specifications

Magnum DS Switchgear Class UL 1066 Low Voltage Power Circuit Breakers

			rms Symmetrical Current Ratings kA 50/60 Hz ①					
Frame Amperes	**Breaker Type Catalog Position 1–6**	**Frame Type**	**Interruption Rating at 254 Vac**	**Interruption Rating at 508 Vac**	**Interruption Rating at 635 Vac**	**Short-Time Withstand Rating**	**Fixed Internal Instantaneous Trip**	**Available Current Sensor and Rating Plugs for Digitrip RMS Trip Unit (Establishes Breaker I_n Rating)**
800	MDN-408	Narrow	42	42	42	42	—	200, 250, 300, 400, 600, 800
	MDN-508	Narrow	50	50	50	50	—	
	MDN-608	Narrow	65	65	65	65	—	
	MDN-C08	Narrow	100	100	65	20	18 x I_n	
	MDS-408	Standard	42	42	42	42	—	
	MDS-508	Standard	50	50	50	50	—	
	MDS-608	Standard	65	65	65	65	—	
	MDS-808	Standard	85	85	85	85	—	
	MDS-C08	Standard	100	100	100	85	85	
	MDS-H08	Standard	130	130	130	85	85	
	MDS-L08 ②	Standard	200	200	200	—	—	
	MDS-X08 ③	Standard	200	200	65	30	30	
1200	MDN-412	Narrow	42	42	42	42	—	200, 250, 300, 400, 600, 800, 1000, 1200
	MDN-512	Narrow	50	50	50	50	—	
	MDN-612	Narrow	65	65	65	65	—	
	MDN-C12	Narrow	100	100	65	25	18 x I_n	
	MDS-X12	Standard	200	200	65	30	30	
	MDS-512	Standard	50	50	50	50	—	
	MDS-612	Standard	65	65	65	65	—	
	MDS-812	Standard	85	85	85	85	—	
	MDS-C12	Standard	100	100	100	85	—	
	MDS-H12	Standard	130	130	130	85	85	
1600	MDN-416	Narrow	42	42	42	42	—	200, 250, 300, 400, 600, 800, 1000, 1200, 1600
	MDN-516	Narrow	50	50	50	50	—	
	MDN-616	Narrow	65	65	65	65	—	
	MDN-C16	Narrow	100	100	65	30	18 x I_n	
	MDS-516	Standard	50	50	50	50	—	
	MDS-616	Standard	65	65	65	65	—	
	MDS-816	Standard	85	85	85	85	—	
	MDS-C16	Standard	100	100	100	85	85	
	MDS-H16	Standard	130	130	130	85	85	
	MDS-L16 ②	Standard	200	200	200	—	—	
	MDS-X16 ③	Standard	200	200	65	30	30	
2000	MDN-620	Narrow	65	65	65	65	—	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000
	MDN-C20	Narrow	100	100	65	35	18 x I_n	
	MDS-620	Standard	65	65	65	65	—	
	MDS-820	Standard	85	85	85	85	—	
	MDS-C20	Standard	100	100	100	85	85	
	MDS-H20	Standard	130	130	130	85	85	
	MDS-L20 ②	Standard	200	200	200	—	—	
	MDS-X20 ③	Standard	200	200	65	30	30	

Notes

① Interrupting ratings shown based on breaker equipped with integral Digitrip RMS trip unit. Interruption ratings for non-automatic breakers are equal to the published short-time withstand rating. These interruption ratings are based on the standard duty cycle consisting of an open operation, a 15-second interval and a close-open operation, in succession, with delayed tripping in case of short-delay devices. The standard duty cycle for short-time ratings consists of maintaining the rated current for two periods of 1/2 seconds each, with a 15-second interval of zero current between the two periods.

② Magnum MDSL current limiting power circuit breaker with integral current limiters. Current Limiter selected determines short-time and fixed instantaneous trip rating. Maximum voltage rating is 600 Vac.

③ Magnum MDSX current limiting power circuit breaker with fast opening contacts.

Magnum DS Switchgear Class UL 1066 Low Voltage Power Circuit Breakers, continued

			rms Symmetrical Current Ratings kA 50/60 Hz ①					
Frame Amperes	**Breaker Type Catalog Position 1–6**	**Frame Type**	**Interruption Rating at 254 Vac**	**Interruption Rating at 508 Vac**	**Interruption Rating at 635 Vac**	**Short-Time Withstand Rating**	**Fixed Internal Instantaneous Trip**	**Available Current Sensor and Rating Plugs for Digitrip RMS Trip Unit (Establishes Breaker I_n Rating)**
2500	MDS-625	Standard	65	65	65	65	—	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000, 2500
	MDS-825	Standard	85	85	85	85	—	
	MDS-C25	Standard	100	100	100	100 ②	85	
	MDS-H25	Standard	130	130	130	85	85	
3200	MDS-632	Standard	65	65	65	65	—	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000, 2500, 3000, 3200
	MDS-832	Standard	85	85	85	85	—	
	MDS-C32	Standard	100	100	100	85	85	
	MDS-H32	Standard	130	130	130	85	85	
	MDS-X32 ③	Double	200	200	④	50	50	
4000	MDN-640	Double narrow	65	65	65	65	—	2000, 2500, 3200, 4000
	MDN-840	Double narrow	85	85	65	85	—	
	MDN-C40	Double narrow	100	100	65	100	—	
	MDS-840	Double	85	85	85	85	—	
	MDS-C40	Double	100	100	100	100	—	
	MDS-H40	Double	130	130	130	130	—	
	MDS-X40 ③	Double	200	200	⑤	50	50	
	MDD-X40	Double	200	200	100	100	—	
5000	MDS-850	Double	85	85	85	85	—	2500, 3200, 4000, 5000
	MDS-C50	Double	100	100	100	100	—	
	MDS-H50	Double	130	130	130	130	—	
	MDS-X50 ③⑤	Double	200	200	④	50	50	
	MDD-X50	Double	200	200	100	100	—	

Notes

① Interruption ratings shown based on breaker equipped with integral Digitrip RMS trip unit. Interruption ratings for non-automatic breakers are equal to the published short-time withstand rating. These interruption ratings are based on the standard duty cycle consisting of an open operation, a 15-second interval and a close-open operation, in succession, with delayed tripping in case of short-delay devices. The standard duty cycle for short-time ratings consists of maintaining the rated current for two periods of 1/2 seconds each, with a 15-second interval of zero current between the two periods.

② Short-time withstand for MDSC at 2500A for 600 Vac is 85 kA.

③ Magnum MDSX current limiting power circuit breaker with fast opening contacts.

④ Product to be tested. Contact Eaton for product rating.

⑤ Breaker applied in a tested fan-cooled enclosure.

Magnum MDSL Current Limiting Power Circuit Breaker

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	
Product Selection	**V4-T3-13**
Technical Data and Specifications	**V4-T3-13**
Trip Curve Charts	**V4-T3-14**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Magnum MDSL Current Limiting Power Circuit Breaker

Product Description

The following curves illustrate the ratings, melting time-current characteristics and current limiting, or let-through characteristics, of limiters for Magnum low voltage power circuit breakers.

The let-through current for a given limiter application is readily determined by extending a vertical line from the applicable maximum available symmetrical fault amperes at the bottom margin to the characteristic line for the particular limiter, and from this intersection extending a horizontal line to the left margin and reading the peak current. The withstand rating of any circuit elements protected by the limiters should be at least equal to this peak current.

It will be noted that the let-through current increases with the limiter size or ampere rating; in other words, the maximum current limiting effect is obtained with the smallest size. This effect is to be expected, since the resistance decreases as the rating increases. If the vertical line from the bottom margin as described in the previous paragraph does not intersect the limiter characteristic line, the available system fault current is below the "threshold" current of that limiter, and it will offer no current limiting effect.

The current limiting principle is illustrated below:

I_a= The Available Peak Fault Current

t_m=The Melting Time

I_p= The Peak Let-Through Current

t_a= The Arcing Time

t_c= The Total Interrupting (Clearing)Time

Current Limiting



Limiter Selection

The selection of a suitable limiter rating for a given application is generally governed by a choice of the following types of protection:

A. Maximum protection of "downstream" components. Type MDSL breakers are often used for this purpose even when the maximum available fault currents are within the interruption rating of the corresponding unfused Magnum breakers.

B. Protection of the circuit breaker only.

Case A would tend to use the smallest available limiter; Case B the largest. When downstream protection is required, the selection is usually a compromise, since certain small limiters cannot be coordinated with the breaker to avoid nuisance blowing on overloads or small and moderate short circuits.

Minimum, recommended and maximum limiter sizes for Magnum MDSL breakers are given in the table on **Page V4-T3-13**.

Product Selection

Magnum MDSL Sensor/Rating Plug vs. Current Limiter Selection ①

Sensor and Rating Plug I_n	MDSL Current Limiter Selection Chart ②									
200	**MA250**	**MA300**	**MA400**	**MA600** ③	**MA800**	**MB1200**	**MB1600**	**MB2000**	**MD2500**	**MD3000**
250			**MA400**	**MA600**	**MA800** ③	**MB1200**	**MB1600**	**MB2000**	**MD2500**	**MD3000**
300			**MA400**	**MA600**	**MA800** ③	**MB1200**	**MB1600**	**MB2000**	**MD2500**	**MD3000**
400				**MA600**	**MA800**	**MB1200** ③	**MB1600**	**MB2000**	**MD2500**	**MD3000**
600					**MA800**	**MB1200**	**MB1600**	**MB2000** ③	**MD2500**	**MD3000**
800						**MB1200**	**MB1600**	**MB2000**	**MD2500** ③	**MD3000**
1000							**MB1600**	**MB2000**	**MD2500** ③	**MD3000**
1200								**MB2000**	**MD2500** ③	**MD3000**
1600										**MD3000** ③
2000										**MD3000** ③

Technical Data and Specifications

Magnum MDSL Ratings

Frame	Catalog Number	Available Sensor/ Rating Plug (Amperes)
800	**MDSL08**	200, 250, 300, 400, 600, 800
1600	**MDSL16**	200, 250, 300, 400, 600, 800, 1000, 1200, 1600
2000	**MDSC20**	1600, 2000

Notes

① Select the current limiter based on the Magnum breaker frame and current sensor and rating plug as shown.

② Refer to MDSL current limiter curves for let-through and time characteristics.

③ The recommended ratings shown as shaded provide for reduced current let-through and breaker coordination within the trip unit settings. Selection of current limiters below the recommended ratings shown provides lower current let-through, however, trip unit settings must be considered to avoid nuisance operation.

Trip Curve Charts

Type Magnum DSL Limiters, Peak Let-Through Current Characteristics



Available Current, rms Symmetrical Amperes x 10

Type Magnum DSL Limiters Average Melting Time-Current Characteristics



Scale x 100 = Current in Amperes

Note

For Time/Current Curves, see www.eaton.com/electrical

Magnum SB Low Voltage Insulated Case Circuit Breaker

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	
Catalog Number Selection	**V4-T3-16**
Technical Data and Specifications	**V4-T3-19**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Magnum SB Low Voltage Insulated Case Circuit Breakers

Product Description

Magnum SB is a low voltage insulated case circuit breaker family designed for the performance and economic requirements of UL 891 switchboards.

- Magnum SB insulated case circuit breakers have interruption ratings up to 130 kA at 635 Vac with continuous current ratings up to 5000 A
- Magnum SB insulated case circuit breakers have lighter-duty short-time withstand ratings and fixed internal instantaneous trips on most ratings, which is characteristic of UL 489 molded case breakers commonly used in UL 891 switchboards. This provides for greater economy and excellent coordination and selectivity for most commercial applications
- Fixed internal instantaneous trips will be phased in on all Magnum SB insulated case circuit breakers rated 3200 A and below to provide an extra safety factor by reducing the energy let-through to downstream circuits at the maximum instantaneous trip point and to facilitate feeder circuit breaker protection in UL 891 switchboards with 3-cycle bus bracing
- Magnum SBSE current limiting power circuit breakers have 150 kA interruption ratings at 480 Vac with continuous current ratings up to 5000 A. The short-time withstand rating is 30 kA for standard frame and 50 kA for double frame breakers



Typical Magnum SB Low Voltage Insulated Case Circuit Breaker Nameplate

Standards and Certifications

UL and ANSI Test Certifications

Magnum SB meets or exceeds the applicable ANSI, NEMA, UL and CSA standards, including:

- ANSI C37.13 (Low Voltage AC Power Circuit Breakers Used in Enclosures)
- ANSI C37.16 (Preferred Ratings, Related Requirements, and Application Recommendations for Low Voltage Power Circuit Breakers and AC Power Circuit Breakers)
- ANSI C37.17 (Trip Devices for AC and General Purpose DC Low Voltage Power Circuit Breakers)
- ANSI C37.50 (Test Procedures for Low Voltage AC Power Circuit Breakers Used in Enclosures)
- UL 1066 (Standard for Low Voltage AC and DC Power Circuit Breakers Used in Enclosures)
- NEMA SG3 (This standard adopts ANSI C37.16 in its entirety)

Comprehensive Enclosure Solutions

Magnum SB has proven performance in Eaton manufactured switchboards with the following test certifications:

- UL 891 (Certified Pow-R-Line C Low Voltage Switchboards)
- UL, CSA 22.2.31 Low Voltage Assemblies

Approvals and Marks

UL listed: Magnum DS Breaker UL File E52096 and Cassette UL File E204565

Product Selection

Contact Eaton for pricing.

Catalog Number Selection

Magnum SB Breaker Product Family

3

SB S 4 12 3 V E A 06 MU

Breaker Type
SB = Magnum switchboard

Frame Type
S = Standard or double
N = Narrow or double narrow
D = MDDX only
E = High endurance

Interrupting/ Withstand Rating
4 = 42
5 = 50
6 = 65
8 = 85
C = 100
H = 130 (DSH)
E = 150 (DSE)
X = 200 (DSX/DDX)
L = 200 (DSL)

Continuous Amperes and Phasing (Facing Front of Breaker)
08 = 800 ABC
12 = 1200 ABC
16 = 1600 ABC
20 = 2000 ABC
25 = 2500 ABC
30 = 3000 ABC
32 = 3200 ABC or ABCABC
3N = 3200 AABBCC
4N = 4000 AABBCC
5N = 5000 AABBCC
40 = 4000 ABCABC
50 = 5000 ABCABC

Poles and Neutral (Facing Front of Breaker)
3 = Three
4 = Four (neutral left)

Mounting Configuration and Load Terminals
H = Fixed horizontal
V = Fixed vertical
L = Drawout (MDN)
W = Drawout (MDS)

Nameplate Language
E = English
A = Spanish

Current Limiter Selection
A = Non-DSL (no limiter)
D = MA250
E = MA300
F = MA400
G = MA600
H = MA800
K = MB1200
L = MB1600
M = MB2000
N = MD2500
P = MD3000

Sensor and Rating Plug Rating
NN = None
01 = 100
02 = 200
05 = 250
03 = 300
04 = 400
06 = 600
08 = 800
10 = 1000
12 = 1200
13 = 1250
16 = 1600
20 = 2000
25 = 2500
30 = 3000
32 = 3200
40 = 4000
50 = 5000

Trip Unit and Protection, and External Control Voltage When Required
NN = Non-automatic (no trip unit)
52 = 520 LSI
5G = 520 LSIG
M2 = 520M LSI
MT = 520M LSI (24/48 Vdc)
MU = 520M LSI (120 Vac)
MV = 520M LSI (240 Vac)
MQ = 520M LSI (125 Vdc)
MG = 520M LSIG
MH = 520M LSIG (24/48 Vdc)
MM = 520M LSIG (120 Vac)
MN = 520 LSIG (240 Vac)
MX = 520M LSIG (125 Vdc)
ME = 520M LSIA (24/48 Vdc)
MC = 520 LSIA (120 Vac)
MF = 520M LSIA (240 Vac)
MZ = 520M LSIA (125 Vdc)
CT = 520MC LSI (24/48 Vdc)
CU = 520MC LSI (120 Vac)
CV = 520MC LSI (240 Vac)
CQ = 520MC LSI (125 Vdc)
CH = 520MC LSIG (24/48 Vdc)
CM = 520MC LSIG (120 Vac)
CN = 520MC LSIG (240 Vac)
CX = 520MC LSIG (125 Vdc)
CE = 520MC LSIA (24/48 Vdc)
CC = 520MC LSIA (120 Vac)
CF = 520MC LSIA (240 Vac)
CY = 520MC LSIA (125 Vdc)
1A = 1150 LSI (24/48 Vdc)
1C = 1150 LSI (120 Vac)
1E = 1150 LSI (240 Vac)
1Q = 1150 LSI (125 Vdc)
1F = 1150 LSIG (24/48 Vdc)
1G = 1150 LSIG (120 Vac)
1H = 1150 LSIG (240 Vac)
1X = 1150 LSIG (125 Vdc)
1J = 1150 LSIA (24/48 Vdc)
1K = 1150 LSIA (120 Vac)
1M = 1150 LSIA (240 Vac)
1Y = 1150 LSIA (125 Vdc)

Magnum SB Breaker Product Family, continued

A W C H N E H K L A X

Shunt Trip (ST)
N = None
A = 110–127 Vac/Vdc
R = 208–240 Vac/Vdc
C = 24 Vdc
H = 48 Vdc
B = 110–127 Vac/Vdc (100% duty)
S = 220–250 Vac/Vdc (100% duty)
D = 24 Vdc (100% duty)
K = 48 Vdc (100% duty)
J = 60 Vdc (100% duty)
6 = 60 Vdc

Motor Operator
M = Manual operated
N = 110–125 Vac (5-sec)
W = 110–125 Vdc (5-sec)
T = 220–250 Vdc (5-sec)
P = 208–277 Vac (5-sec)
L = 24 Vdc (5-sec)
K = 48 Vdc (5-sec)
S = 60 Vdc (5-sec)
1 = 110–125 Vac (3-sec)
2 = 220–250 Vac (3-sec)
4 = 24 Vdc (3-sec)
8 = 48 Vdc (3-sec)
5 = 110–125 Vdc (3-sec)
9 = 220–250 Vdc (3-sec)

Spring Release Device (SRD)
N = None
A = 110–127 Vac/Vdc
R = 208–240 Vac/Vdc
C = 24 Vdc
H = 48 Vdc
S = 60 Vdc

Undervoltage Release (UVR) or 2nd Shunt Trip (ST)
N = None
A = UVR (110–127 Vac)
R = UVR (208–240 Vac)
C = UVR (24 Vdc)
H = UVR (48 Vdc)
D = UVR (60 Vdc)
E = UVR (110–125 Vdc)
F = UVR (220–250 Vdc)
G = UVR (32 Vdc)
X = UVR (380–415 Vac)
J = UVR (480 Vac)
K = UVR (600 Vac)
1 = 2nd ST (110–127 Vac/Vdc)
2 = 2nd ST (208–250 Vac/Vdc)
3 = 2nd ST (24 Vdc)
4 = 2nd ST (48 Vdc)
6 = 2nd ST (60 Vdc)
B = 2nd ST (110–127 Vac/Vdc 100% duty)
O = 2nd ST (220–250 Vac/Vdc 100% duty)
I = 2nd ST (24 Vdc 100% duty)
Q = 2nd ST (48 Vdc 100% duty)
9 = 2nd ST (60 Vdc 100% duty)

Auxiliary Switch
N = None
2 = 2A/2B
4 = 4A/4B
6 = 6A/6B

Bell Alarms Switch (OTS) with 2a/2b Contacts and/or Mechanical Trip Indicator

	Mech. Trip Indicator	Mech. Interlock for Manual Reset	OTS Switch with Two Form C Contacts
E =	No	—	No
N =	Yes	No	No
Y =	Yes	No	Yes
M =	Yes	Yes	No
L =	Yes	Yes	Yes
F =	Yes	No	Yes with 24 V reset
G =	Yes	No	Yes with 120 V reset
H =	Yes	No	Yes with 240 V reset
I =	Yes	Yes	Yes with 24 V reset
J =	Yes	Yes	Yes with 120 V reset
K =	Yes	Yes	Yes with 240 V reset

Padlock Provisions for Blocking Close and/or Open ACB Manual Pushbuttons
N = None
M = Metal (block close and open)
P = Plastic (block close and open)
C = Metal (block close only)
H = Plastic (block close only)
S = Metal swbd lock-off (block close, depress open)

Operations Counter and/or Keylock Provisions

	Counter	Keylock Provisions
N =	No counter	No locks
K =	No counter	Kirk lock
C =	No counter	Castell lock
R =	No counter	Ronis lock
S =	No counter	CES lock
A =	Counter	No lock
Y =	Counter	Kirk lock
L =	Counter	Castell lock
H =	Counter	Ronis lock indicator
E =	Counter	CES lock

Latch Check Switch/Trip Unit Metering Voltage Connection for Digitrip 1150 Trip Unit

	Latch Check Switch	1150 Voltage Connection
N =	None	Upper terminals
M =	None	Lower terminals
L =	LCS wired to SRD	Upper terminals
Y =	LCS Wired to SRD	Lower terminals
C =	LCS Wired External	Upper terminals
D =	LCS Wired External	Lower terminals

Breaker Shipping Options and Instructions
A = Fixed breaker alone with door kit
B = Fixed breaker alone with door kit and pre-wired
F = Fixed breaker alone without door kit
A = Drawout breaker alone without door frame kit
C = Drawout breaker in cassette (un-wired)
P = Drawout breaker in cassette (shutters)
S = Drawout breaker in cassette (shutters)
W = Drawout breaker in cassette (pre-wired and shutters)
Double frame drawout breakers ship without cassette drawout. ACBs ship in narrow and universal cassettes only.

Frame Use
X = All breakers

Cassette Magnum SB Breaker Product Family

M E 32 3 C A DN N NNN W C

Cassette Family
M = Standard or double frame
L = Narrow frame only

Interrupt Type
E = SB cassette (150 kAIC)
N = Cassettes (up to 100 kA)

Continuous Amperes
16 = Up to 1600 A
20 = Up to 2000 A
32 = 2500 to 3200 A
40 = 4000 to 1600 A
50 = 5000 to 2000 A

Poles
3 = Three-pole
4 = Four-pole

Cassette Frame and Rear Terminals
P = Basic cassette (without vertical bus stabs)
C = Basic cassette with stabs (with vertical bus stab kit)
H = Narrow frame cassette (with horizontal terminal pads)
U = Universal cassette (with universal terminal pads)

Arc Hood
A = Arc hood installed

Door Frame and Gasket Kit
DN = Door frame and gasket kit included
XN = Door frame and gasket kit not included

Shutters
N = No shutters
S = Shutters installed

Future Use
NNN = All cassettes

Cassette Wiring
N = Un-wired
W = Cassette wired

Cassette Shipping
C = Cassette only
B = Breaker shipped in cassette

Technical Data and Specifications

Magnum SB Switchboard Class Insulated Case Low Voltage Air Circuit Breakers

			rms Symmetrical Current Ratings kA 50/60 Hz ①					
Frame Amperes	**Breaker Type Catalog Position 1–6**	**Frame Type**	**Interruption Rating at 254 Vac**	**Interruption Rating at 508 Vac**	**Interruption Rating at 635 Vac**	**Short-Time Withstand Rating**	**Fixed Internal Instantaneous Trip**	**Available Current Sensor and Rating Plugs for Digitrip RMS Trip Unit (Establishes Breaker I_n Rating)**
800	SBN-508	Narrow	50	50	35	20	18 x I_n	200, 250, 300, 400, 600, 800
	SBN-608	Narrow	65	65	42	20	18 x I_n	
	SBN-C08	Narrow	100	100	65	20	18 x I_n	
	SBS-608	Standard	65	65	65	20	18 x I_n	
	SBS-808	Standard	85	85	85	20	18 x I_n	
	SBS-C08	Standard	100	100	85	20	18 x I_n	
	SBS-H08	Standard	130	130	130	20	18 x I_n	
	SBS-E08 ②③	Standard	200	150	65	30	30	
1200	SBN-512	Narrow	50	50	35	25	18 x I_n	200, 250, 300, 400, 600, 800, 1000, 1200
	SBN-612	Narrow	65	65	42	25	18 x I_n	
	SBN-C12	Narrow	100	100	65	25	18 x I_n	
	SBS-612	Standard	65	65	65	25	18 x I_n	
	SBS-812	Standard	85	85	85	25	18 x I_n	
	SBS-C12	Standard	100	100	85	25	18 x I_n	
	SBS-H12	Standard	130	130	130	25	18 x I_n	
	SBS-E12 ②	Standard	200	150	65	30	30	
1600	SBN-516	Narrow	50	50	35	30	18 x I_n	200, 250, 300, 400, 600, 800, 1000, 1200, 1600
	SBN-616	Narrow	65	65	42	30	18 x I_n	
	SBN-C16	Narrow	100	100	65	30	18 x I_n	
	SBS-616	Standard	65	65	65	30	18 x I_n	
	SBS-816	Standard	85	85	85	30	18 x I_n	
	SBS-C16	Standard	100	100	85	30	18 x I_n	
	SBS-H16	Standard	130	130	130	30	18 x I_n	
	SBS-E16 ②	Standard	200	150	65	30	30	
2000	SBN-620	Narrow	65	65	65	35	18 x I_n	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000
	SBN-C20	Narrow	100	100	65	35	18 x I_n	
	SBS-620	Standard	65	65	65	35	18 x I_n	
	SBS-820	Standard	85	85	85	35	18 x I_n	
	SBS-C20	Standard	100	100	85	35	18 x I_n	
	SBS-H20	Standard	130	130	130	35	18 x I_n	
	SBS-E20 ②	Standard	200	150	65	30	30	

Notes

① Interruption ratings shown based on breaker equipped with integral Digitrip RMS trip unit. Interruption ratings for non-automatic breakers are equal to the published short-time withstand rating. These interruption ratings are based on the standard duty cycle consisting of an open operation, a 15-second interval and a close-open operation, in succession, with delayed tripping in case of short-delay devices. The standard duty cycle for short-time ratings consists of maintaining the rated current for two periods of 1/2 seconds each, with a 15-second interval of zero current between the two periods.

② Magnum SBSE current limiting power circuit breaker with fast opening contacts.

③ Not released.

④ Product to be tested. Contact Eaton for product rating.

⑤ Breaker applied in a tested fan-cooled enclosure.

Magnum SB is UL 1066 listed.

Magnum SB Switchboard Class Insulated Case Low Voltage Air Circuit Breakers, continued

			rms Symmetrical Current Ratings kA 50/60 Hz ①					
Frame Amperes	**Breaker Type Catalog Position 1–6**	**Frame Type**	**Interruption Rating at 254 Vac**	**Interruption Rating at 508 Vac**	**Interruption Rating at 635 Vac**	**Short-Time Withstand Rating**	**Fixed Internal Instantaneous Trip**	**Available Current Sensor and Rating Plugs for Digitrip RMS Trip Unit (Establishes Breaker I_n Rating)**
2500	SBS-625	Standard	65	65	65	45	18 x I_n	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000, 2500
	SBS-825	Standard	85	85	85	45	18 x I_n	
	SBS-C25	Standard	100	100	85	45	18 x I_n	
	SBS-H25	Standard	130	130	130	45	18 x I_n	
	SBS-E25 ②	Double	200	150	④	50	50	
3000	SBS-630	Standard	65	65	65	50	18 x I_n	200, 250, 300, 400, 600, 800, 1000, 1200, 1600, 2000, 2500, 3000
	SBS-830	Standard	85	85	85	50	18 x I_n	
	SBS-C30	Standard	100	100	85	50	18 x I_n	
	SBS-H30	Standard	130	130	130	50	18 x I_n	
	SBS-E30 ②	Double	200	150	④	50	50	
4000	SBS-840	Double	85	85	85	72	18 x I_n	2000, 2500, 3000, 4000
	SBS-C40	Double	100	100	100	72	18 x I_n	
	SBS-H40	Double	130	130	130	72	18 x I_n	
	SBN-840	Double Narrow	85	85	65	72/65	18 x I_n	
	SBN-C40	Double Narrow	100	100	65	72/65	18 x I_n	
	SBS-E40 ②	Double	200	150	④	50	50	
5000	SBS-850	Double	85	85	85	85	18 x I_n	2500, 3000, 4000, 5000
	SBS-C50	Double	100	100	100	90	18 x I_n	
	SBS-H50	Double	130	130	130	90	18 x I_n	
	SBS-E50 ②③	Double	200	150	④	50	50	

Notes

① Interruption ratings shown based on breaker equipped with integral Digitrip RMS trip unit. Interruption ratings for non-automatic breakers are equal to the published short-time withstand rating. These interruption ratings are based on the standard duty cycle consisting of an open operation, a 15-second interval and a close-open operation, in succession, with delayed tripping in case of short-delay devices. The standard duty cycle for short-time ratings consists of maintaining the rated current for two periods of 1/2 seconds each, with a 15-second interval of zero current between the two periods.

② Magnum SBSE current limiting power circuit breaker with fast opening contacts.

③ Breaker applied in a tested fan-cooled enclosure.

④ Product to be tested. Contact Eaton for product rating.

Magnum SB is UL 1066 listed.

Digitrip Trip Units for Magnum DS and SB ANSI/UL Rated Power Circuit Breakers

Trip Unit Type		Digitrip 520	Digitrip 520M	Digitrip 520MC	Digitrip 1150+ ①
Ampere range		200–5000 A	200–5000 A	200–5000 A	200–5000 A
Interruption rating at 480 V		42–200 kA	42–200 kA	42–200 kA	42–200 kA
rms sensing		Yes	Yes	Yes	Yes
Protection and Coordination					
Protection	Ordering options	LI, LSI, LSIG, LSIA	LSI, LSIG	LSI, LSIG	LSI, LSIG, LSIA
	Fixed rating plug (I_n)	Yes	Yes	Yes	Yes
	Overtemperature trip	Yes	Yes	Yes	Yes
Long delay protection (L)	Long delay pickup	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)
	Long delay time I^2t at 6 x I_r	2–24 sec	2–24 sec	2–24 sec	2–24 sec
	Long delay time I^4t	No	No	No	1–5 sec
	IEEE curves	No	No	No	Yes
	Long delay thermal memory	Yes	Yes	Yes	Yes
	High load alarm	No	No	No	0.5–1.0 x (I_r)
Short delay protection (S)	Short delay pickup	200–1000% x (I_r) and M1	200–1000% x (I_r) and M1	200–1000% x (I_r) and M1	200–1000% x (I_r) and M1
	Short delay time I^2t at 8 x I_r	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Short delay time flat	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Short delay time ZSI	Yes	Yes	Yes	Yes
Instantaneous protection (I)	Instantaneous pickup	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1
	Making current release	Yes	Yes	Yes	Yes
	Off position	Yes	Yes	Yes	Yes
Ground fault protection (G) ②	Ground fault alarm	No	Yes	Yes	Yes
	Ground fault pickup	25–100% x (I_n)	25–100% x (I_n)	25–100% x (I_n)	24–100% x (I_n)
	Ground fault delay I^2t at 0.625 x I_n	100–500 ms	100–500 ms	100–500 ms	100–500 ms
Disable ground fault protection		No	No	No	No
Neutral protection (N)		Model LSI only	Model LSI only	Model LSI only	Model LSI only
System Diagnostics					
Cause of trip LEDs		Yes	Yes	Yes	Yes
Magnitude of trip information		No	Yes	Yes	Yes
Remote signal contacts		No	Yes	Yes	Yes
Programmable contacts		No	No	No	Yes
Electronic operations counter		No	No	No	Yes

Notes

① Over and undervoltage alarm or trip, over and underfrequency alarm or trip, voltage unbalance alarm or trip, reverse power trip and phase rotation alarm are included.

② 1200 A maximum ground fault setting per UL/NEC.

I_n = Rating plug and sensor rating.
I_r = Long delay pickup setting.

Digitrip Trip Units for Magnum DS and SB ANSI/UL Rated Power Circuit Breakers, continued

Trip Unit Type	Digitrip 520	Digitrip 520M	Digitrip 520MC	Digitrip 1150+ ①
System Monitoring				
Digital display	No	4-Character LCD	4-Character LCD	24-Character LED
Current (%) full scale sensor	No	Yes +/– 2%	Yes +/– 2%	Yes +/– 1%
Voltage (%) L to L	No	No	No	Yes +/– 1%
Power and energy (%)	No	No	No	Yes +/– 2%
Apparent power kVA and demand	No	No	No	Yes
Reactive power kVAR	No	No	No	Yes
Power factor	No	No	No	Yes
Crest factor	No	No	No	Yes
System Communications				
Type	—	—	INCOM/PowerNet/Modbus ②/ PROFIBUS ②	INCOM/PowerNet/TripLink/ Modbus ②/PROFIBUS ②
Power supply in breaker	N/A	Optional	Standard	Standard
Additional Features				
Trip log (three events)	No	No	No	Yes
Electronic operations counter	No	No	No	Yes
Testing method ③	Test set	Test set	Test set	Integral and test set
Waveform capture	No	No	No	Yes
Arcflash Reduction Maintenance System Mode	No	No	Yes	Yes ④
Breaker health monitor	No	No	No	Yes
Programmable relay functions	No	No	No	Yes ①

Notes

① Over and undervoltage alarm or trip, over and underfrequency alarm or trip, voltage unbalance alarm or trip, reverse power trip and phase rotation alarm are included.
② Requires externally mounted MMINT or PMINT module.
③ Test set for secondary injection.
④ Contact Eaton for availability.

I_n = Rating plug and sensor rating.
I_r = Long delay pickup setting.

Magnum IEC Double Narrow Frame Drawout Air Circuit Breaker, With Cassette

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	
Catalog Number Selection	**V4-T3-24**
Technical Data and Specifications	**V4-T3-27**
Magnum Options and Accessories	**V4-T3-30**
Wiring Diagrams	**V4-T3-32**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Magnum IEC Rated Air Circuit Breakers

Product Description

Magnum air circuit breakers are designed to enable global power distribution solutions in IEC switchboards and other custom enclosures.

- Magnum IEC air circuit breakers have interruption ratings up to 100 kA at 690 Vac with continuous current ratings up to 6300 A
- Magnum IEC air circuit breaker continuous current frames are 100% rated. No thermal de-rating is required when applying the breaker in the low voltage systems enclosure at ambient temperatures of 104 °F (40 °C)
- Magnum IEC breakers carry the KEMA Keur Mark, which requires periodic follow-up testing, witnessed by KEMA, to demonstrate our product performs to its published nameplate ratings. This differentiates Magnum air circuit breakers from the competition, where in general, self-certification testing is performed on products when initially introduced with no binding commitments to perform subsequent follow-up third-party testing

Standards and Certifications

IEC Test Certifications

Magnum air circuit breakers meet or exceed the applicable IEC standards, including:

- EN/IEC 60947-2
- KEMA third-party witness and follow-up testing

Comprehensive Enclosure Solutions

Magnum air circuit breakers have proven performance in IEC switchboards and custom enclosures manufactured by Eaton and Low Voltage Systems Builders (OEMs) to the following standards:

- EN/IEC 60947-1
- EN/IEC 60439-1
- Eaton manufactured IEC Low Voltage Switchboard solutions include:
  - Eaton MEM M-Form (UK) Low Voltage Switchboards
  - Eaton Holec® Capitole 40 and Capitole 20 (Holland) Low Voltage Switchboards
  - Eaton Tabula Low Voltage Switchboard Systems (global) for Low Voltage Systems Builders
  - Eaton Elatis (Germany) Low Voltage Switchboards
  - Eaton Xenergy and Modan switchboard systems (global) for low voltage systems builders

Approvals and Marks

Magnum air circuit breakers carry the following approvals and approval marks:

- CE
- KEMA Keur mark
- ABS (American Bureau of Shipping) Type Listed Certificate Number 04-HS422844B-PDA-DUB
- CCC (Certificate for China Compulsory Product Certification) to GB14048.2-2001, Certificate Numbers:
  - 2005010307139381
  - 2003010307094561
  - 2003010307094558
- American Bureau of Shipping (ABS)
- Det Norske Veritas (DNV)
- Lloyds of London
- South African Bureau of Standards (SABS)
- For a complete and comprehensive listing of all low voltage power breakers, please visit www.eaton.com

CE KEMA KEUR

Note: The KEMA Keur Mark on the Magnum ACB Label Confirms Third-Party Witness and Follow-up Testing

Catalog Number Selection

Magnum IEC Breaker Product Family ①

MW N 5 12 4 V E A 03 MT 6 M C J 2 Y C N M W X

Breaker Frame
- **I** = Standard or double
- **N** = Narrow or double narrow
- **K** = Special 1100 Vac ACB

Interrupting I_{cu}
- **4** = 40 kV
- **5** = 50 kV
- **6** = 65 kV
- **8** = 85 kV
- **C** = 100 kV
- **Z** = 25 kV (1100 Vac MWK)

Continuous Amperes and Phasing (Facing Front of Breaker)
- **08** = 800 ABC
- **10** = 1000 ABC
- **12** = 1250 ABC
- **16** = 1600 ABC
- **20** = 2000 ABC
- **25** = 2500 ABC
- **32** = 3200 ABC
- **41** = 4000 ABC (standard drawout only)
- **4N** = 4000 AABBCC
- **5N** = 5000 AABBCC
- **6N** = 6300 AABBCC
- **40** = 4000 ABCABC
- **50** = 5000 ABCABC
- **60** = 6300 ABCABC

Poles and Neutral (Facing Front of Breaker)
- **3** = Three
- **4** = Four (neutral left)
- **R** = Four (reserved for neutral right)

Mounting Configuration and Load Terminals
- **H** = Fixed horizontal
- **V** = Fixed vertical
- **L** = Drawout horizontal

Nameplate Language
- **E** = English
- **A** = Spanish

Sensor and Rating Plug Rating
- **NN** = None
- **02** = 200
- **05** = 250
- **03** = 300
- **04** = 400
- **06** = 600
- **07** = 630
- **08** = 800
- **10** = 1000
- **12** = 1200
- **13** = 1250
- **16** = 1600
- **20** = 2000
- **25** = 2500
- **30** = 3000
- **32** = 3200
- **40** = 4000
- **50** = 5000
- **63** = 6300

Trip Unit and Protection, (and External Control Voltage When Required)
- **NN** = Non-automatic (no trip unit)
- **22** = 520 LI
- **52** = 520 LSI
- **5W** = 520i LSIG
- **M2** = 520M LSI
- **MT** = 520M LSI (24–48 Vdc)
- **MU** = 520M LSI (120 Vac)
- **MV** = 520M LSI (240 Vac)
- **MW** = 520Mi LSIG
- **MJ** = 520Mi LSIG (24–48 Vdc)
- **MK** = 520Mi LSIG (120 Vac)
- **ML** = 520Mi LSIG (240 Vac)
- **ME** = 520M LSIA (24–48 Vdc)
- **MC** = 520M LSIA (120 Vac)
- **MF** = 520M LSIA (240 Vac)
- **CT** = 520MC LSI (24–48 Vdc)
- **CU** = 520MC LSI (120 Vac)
- **CV** = 520MC LSI (240 Vac)
- **CE** = 520MC LSIA (24–48 Vdc)
- **CC** = 520MC LSIA (120 Vac)
- **CF** = 520MC LSIA (240 Vac)
- **CJ** = 520MCi LSIG (24–48 Vdc)
- **CK** = 520MCi LSIG (120 Vac)
- **CF** = 520MCi LSIG (240 Vac)
- **C1** = 520MC Arcflash Reduction Maintenance System LSI (24–48 Vdc)
- **C2** = 520MC Arcflash Reduction Maintenance System LSI (120 Vac)
- **C3** = 520MC Arcflash Reduction Maintenance System LSI (240 Vac)
- **C4** = 520MC Arcflash Reduction Maintenance System LSIA (24–48 Vdc)
- **C5** = 520MC Arcflash Reduction Maintenance System LSIA (120 Vac)
- **C6** = 520MC Arcflash Reduction Maintenance System LSIA (240 Vac)
- **C7** = 520MC Arcflash Reduction Maintenance System LSIG (24–48 Vdc)
- **C8** = 520MC Arcflash Reduction Maintenance System LSIG (120 Vac)
- **C9** = 520MC Arcflash Reduction Maintenance System LSIG (240 Vac)
- **1W** = 1150i LSI (24–48 Vdc)
- **1N** = 1150i LSI (120 Vac)
- **1P** = 1150i LSI (240 Vac)
- **1R** = 1150i LSIG/A (24–48 Vdc)
- **1S** = 1150i LSIG/A (120 Vac)
- **1T** = 1150i LSIG/A (240 Vac)

Note

① Exclusionary rules apply. Refer to price list. Confirm all final part numbers with Eaton. Format structure subject to modifications and additions without notice.

Magnum IEC Breaker Product Family, continued ①

MW N 5 12 4 V E A 03 MT 6 M C J 2 Y C N M W X

Shunt Trip Attachment (STA)
- **N** = None
- **A** = 110–127 Vac/Vdc
- **R** = 208–240 Vac/Vdc
- **C** = 24 Vdc
- **H** = 48 Vdc
- **B** = 110–127 Vac/Vdc (100% duty)
- **S** = 220–250 Vac/Vdc (100% duty)
- **D** = 24 Vdc (100% duty)
- **K** = 48 Vdc (100% duty)
- **J** = 60 Vdc (100% duty)
- **6** = 60 Vdc

Motor Operator
- **M** = Manual operated
- **N** = 110–125 Vac (5-sec)
- **W** = 110–125 Vdc (5-sec)
- **T** = 220–250 Vdc (5-sec)
- **P** = 208–277 Vac (5-sec)
- **L** = 24 Vdc (5-sec)
- **K** = 48 Vdc (5-sec)
- **S** = 60 Vdc (5-sec)
- **1** = 110–125 Vac (3-sec)
- **2** = 220–250 Vac (3-sec)
- **4** = 24 Vdc (3-sec)
- **8** = 48 Vdc (3-sec)
- **5** = 110–125 Vdc (3-sec)
- **9** = 220–250 Vdc (3-sec)

Spring Release Device (SRD)
- **N** = None
- **A** = 110–127 Vac/Vdc
- **R** = 208–240 Vac/Vdc
- **C** = 24 Vdc
- **H** = 48 Vdc
- **S** = 60 Vdc

Undervoltage Release (UVR) or 2nd Shunt Trip (ST)
- **N** = None
- **A** = UVR (110–127 Vac)
- **R** = UVR (208–240 Vac)
- **C** = UVR (24 Vdc)
- **H** = UVR (48 Vdc)
- **D** = UVR (60 Vdc)
- **E** = UVR (110–125 Vdc)
- **F** = UVR (220–250 Vdc)
- **G** = UVR (32 Vdc)
- **X** = UVR (380–415 Vac)
- **J** = UVR (480 Vac)
- **K** = UVR (600 Vac)
- **1** = 2nd ST (110–127 Vac/Vdc)
- **2** = 2nd ST (208–250 Vac/Vdc)
- **3** = 2nd ST (24 Vdc)
- **4** = 2nd ST (48 Vdc)
- **6** = 2nd ST (60 Vdc)
- **B** = 2nd ST (110–127 Vac/Vdc 100% duty)
- **O** = 2nd ST (220–250 Vac/Vdc 100% duty)
- **I** = 2nd ST (24 Vdc 100% duty)
- **Q** = 2nd ST (48 Vdc 100% duty)
- **9** = 2nd ST (60 Vdc 100% duty)

Auxiliary Switch
- **N** = None
- **2** = 2A/2B
- **4** = 2A/2B
- **6** = 2A/2B

Bell Alarms Switch (OTS) with 2a/2b Contacts and/or Mechanical Trip Indicator

	Mech. Trip Indicator	Mech. Interlock for Manual Reset	OTS Switch with Two Form C Contacts
E =	No	—	No
N =	Yes	No	No
Y =	Yes	No	Yes
M =	Yes	Yes	No
L =	Yes	Yes	Yes
F =	Yes	No	Yes with 24 V reset
G =	Yes	No	Yes with 120 V reset
H =	Yes	No	Yes with 240 V reset
I =	Yes	Yes	Yes with 24 V reset
J =	Yes	Yes	Yes with 120 V reset
K =	Yes	Yes	Yes with 240 V reset

Padlock Provisions for Blocking Close and/or Open ACB Manual Pushbuttons
- **N** = None
- **M** = Metal (block close and open)
- **P** = Plastic (block close and open)
- **C** = Metal (block close only)
- **H** = Plastic (block close only)

Operations Counter and/or Keylock Provisions

	Counter	Keylock Provisions
N =	No counter	No locks
K =	No counter	Kirk lock
C =	No counter	Castell lock
R =	No counter	Ronis lock
S =	No counter	CES lock
A =	Counter	No lock
Y =	Counter	Kirk lock
L =	Counter	Castell lock
H =	Counter	Ronis lock indicator
E =	Counter	CES lock

Latch Checking Switch/Trip Unit Metering Voltage Connection for Digitrip 1150 Trip Unit

Latch Check Switch	1150 Voltage Connection
N = None	Upper terminals
M = None	Lower terminals
L = LCS wired to SRD	Upper terminals
Y = LCS wired to SRD	Lower terminals
C = LCS wired external	Upper terminals
D = LCS wired external	Lower terminals

ACB Shipping Instructions
- **A** = Fixed ACB with door kit
- **B** = Fixed breaker alone with door kit and pre-wired
- **F** = Fixed ACB without door kit
- **A** = D/O ACB only without door kit
- **C** = D/O ACB in cassette (un-wired)
- **P** = D/O ACB in cassette (pre-wired)
- **S** = D/O ACB in cassette (shutters)
- **W** = D/O ACB in cassette (pre-wired and shutters)

Double frame D/O ACBs ship without cassette

Future Use
- **X** = All ACBs

Note

① Exclusionary rules apply. Refer to price list. Confirm all final part numbers with Eaton. Format structure subject to modifications and additions without notice.

Cassette Magnum IEC Breaker Product Family ①



Note

① Exclusionary rules apply. Refer to price list. Confirm all final part numbers with Eaton. Format structure subject to modifications and additions without notice.

Technical Data and Specifications

Magnum IEC 60947-2 Rated Air Circuit Breakers

Frame Amperes	Breaker Type Catalog Position 1–6	Frame Type	rms Symmetrical Current Ratings kA ① Interruption Rating at 240 Vac $I_{cu} = I_{cs}$	Interruption Rating at 440 Vac $I_{cu} = I_{cs}$	Interruption Rating at 690 Vac $I_{cu} = I_{cs}$	Withstand Rating I_{cw} 1-Sec / 3-Sec	Fixed Internal Instantaneous Trip	Available Current Sensor and Rating Plugs for Digitrip RMS Trip Unit (Establishes Breaker I_n Rating)
800	MWN-508	Narrow	50	50	50	50/—	—	200, 250, 300, 400, 630, 800
	MWN-608	Narrow	65	65	65	65/40	—	
	MWI-608	Standard	65	65	65	65/—	—	
	MWI-808	Standard	85	85	85	85/65	—	
	MWI-C08	Standard	100	100	85	85/65	85	
1000	MWN-410	Narrow	40	40	40	40/—	—	200, 250, 300, 400, 630, 800, 1000
	MWN-510	Narrow	50	50	50	50/—	—	
	MWN-610	Narrow	65	65	65	65/40	—	
	MWI-610	Standard	65	65	65	65/—	—	
	MWI-810	Standard	85	85	85	85/65	—	
	MWI-C10	Standard	100	100	85	85/65	85	
1250	MWN-412	Narrow	40	40	40	40/—	—	200, 250, 300, 400, 630, 800, 1000, 1250
	MWN-512	Narrow	50	50	50	50/—	—	
	MWN-612	Narrow	65	65	65	65/40	—	
	MWI-612	Standard	65	65	65	65/—	—	
	MWI-812	Standard	85	85	85	85/65	—	
	MWI-C12	Standard	100	100	85	85/65	85	
1600	MWN-516	Narrow	50	50	50	50/—	—	200, 250, 300, 400, 630, 800, 1000, 1250, 1600
	MWN-616	Narrow	65	65	65	65/40	—	
	MWI-616	Standard	65	65	65	65/—	—	
	MWI-816	Standard	85	85	85	85/65	—	
	MWI-C16	Standard	100	100	85	85/65	85	
2000	MWN-520	Narrow	50	50	50	50/30	—	200, 250, 300, 400, 630, 800, 1000, 1250, 1600, 2000
	MWN-620	Narrow	65	65	65	65/40	—	
	MWI-620	Standard	65	65	65	65/50	—	
	MWI-820	Standard	85	85	85	85/65	—	
	MWI-C20	Standard	100	100	85	85/65	85	
2500	MWI-625	Standard	65	65	65	65/—	—	200, 250, 300, 400, 630, 800, 1000, 1250, 1600, 2000, 2500
	MWI-825	Standard	85	85	85	85/65	—	
	MWI-C25	Standard	100	100	85	85/65	85	
	MWI-H25	Standard	125	125	125	85/65	—	
3200	MWI-632	Standard	65	65	65	65/50	—	200, 250, 300, 400, 630, 800, 1000, 1250, 1600, 2000, 2500, 3200
	MWI-832	Standard	85	85	85	85/65	—	
	MWI-C32	Standard	100	100	85	85/65	85	
	MWI-H32	Standard	—	—	125	—	—	
4000	MWI-641 ②	Standard	65	65	65	65/50	—	2000, 2500, 3200, 4000
	MWI-841 ②	Standard	85	85	85	85/65	—	
	MWI-C41 ②	Standard	105	105	85	85/65	—	
	MWN-64N	Double narrow	65	65	65	65/—	—	
	MWN-84N	Double narrow	85	85	65	85/—	—	
	MWN-C4N	Double narrow	100	100	65	100/—	—	
	MWI-64N	Double	65	65	65	65/—	—	
	MWI-84N	Double	85	85	85	85/—	—	
	MWI-C4N	Double	100	100	100	100/—	—	
5000	MWI-85N	Double	85	85	85	85/—	—	2500, 3200, 4000, 5000
	MWI-C5N	Double	100	100	100	100/—	—	
6300	MWI-86N	Double	85	85	85	85/—	—	3200, 4000, 5000, 6300
	MWI-C6N	Double	100	100	100	100/—	—	

Notes

① Interruption ratings shown based on breaker equipped with integral Digitrip RMS Trip Unit. Interruption ratings for non-automatic breakers are equal to the published breaker I_{cw} rating.

② Magnum IEC standard frame breakers rated for 4000 A continuous current are available in drawout configuration only.

Digitrip Trip Units for Magnum IEC Rated Air Circuit Breakers

Trip Unit Type		Digitrip 520*i*	Digitrip 520M*i*	Digitrip 520MC*i*	Digitrip 1150*i*+ ①
Ampere range		200–6300 A	200–6300 A	200–6300 A	200–6300 A
Interruption rating at 690 V		40–100 kA	40–100 kA	40–100 kA	40–100 kA
rms sensing		Yes	Yes	Yes	Yes
Protection and Coordination					
Protection	Ordering options	LI, LSI, LSIG, LSIA	LSI, LSIG	LSI, LSIG	LSI, LSIG, LSIA
	Fixed rating plug (I_n)	Yes	Yes	Yes	Yes
	Overtemperature trip	Yes	Yes	Yes	Yes
Long delay protection (L)	Long delay setting	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)	0.4–1.0 x (I_n)
	Long delay time I^2t at 6 x I_r	2–24 sec	2–24 sec	2–24 sec	2–24 sec
	Long delay time I^4t	No	No	No	1–5 sec
	IEC Type A, B, C curves	No	No	No	Yes
	Long delay thermal memory	Yes	Yes	Yes	Yes
	High load alarm	No	No	No	0.7–1.0 x I_r
Short delay protection (S)	Short delay pickup	200–1000% x (I_r) and M1	200–1000% x (I_r) and M1	200–1000% x (I_r) and M1	150–1000% x (I_r) and M1
	Short delay time I^2t at 8 x I_r	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Short delay time flat	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Short delay time ZSI	Yes	Yes	Yes	Yes
Instantaneous protection (I)	Instantaneous pickup	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1	200–1000% x (I_n) and M1
	Making current release	Yes	Yes	Yes	Yes
	Off position	Yes	Yes	Yes	Yes
Earth fault protection (G)	Earth fault alarm	No	Yes	Yes	Yes
	Earth fault pickup	25–100% x (I_n)	25–100% x (I_n)	25–100% x (I_n)	24–100% x (I_n)
	Earth fault delay I^2t at 0.625 x I_n	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Earth fault delay flat	100–500 ms	100–500 ms	100–500 ms	100–500 ms
	Earth fault ZSI	Yes	Yes	Yes	Yes
	Earth fault memory	Yes	Yes	Yes	Yes
Disable ground fault protection		No	No	No	Yes
Neutral protection (N)		Model LSI only	Model LSI only	Model LSI only	Model LSI only
System Diagnostics					
Cause of trip LEDs		Yes	Yes	Yes	Yes
Magnitude of trip information		No	No	No	Yes
Remote signal contacts		No	Yes	Yes	Yes
Programmable contacts		No	No	No	2

Notes

① Over and undervoltage alarm or trip, over and underfrequency alarm or trip, voltage unbalance alarm or trip, reverse power trip and phase rotation alarm are included.

I_n = Rating plug rating.
I_r = LDPU setting.

i Trip units are only used on IEC breakers with earth fault.

Digitrip Trip Units for Magnum IEC Rated Air Circuit Breakers, continued

Trip Unit Type	Digitrip 520*i*	Digitrip 520M*i*	Digitrip 520MC*i*	Digitrip 1150*i*+ ①
System Monitoring				
Digital display	No	4-Character LCD	4-Character LCD	24-Character LED
Current (%) full scale sensor	No	Yes +/– 2%	Yes +/– 2%	Yes +/– 1%
Voltage (%) L to L	No	No	No	Yes +/– 1%
Power and energy (%)	No	No	No	Yes +/– 2%
Apparent power kVA and demand	No	No	No	Yes
Reactive power kVAR	No	No	No	Yes
Power factor	No	No	No	Yes
Crest factor	No	No	No	Yes
Power quality—harmonics	No	No	No	Yes
% THD	No	No	No	Yes
System Communications				
Type	—	—	INCOM/PowerNet/Modbus ②/ PROFIBUS ②	INCOM/PowerNet/TripLink/ Modbus ②/PROFIBUS ②
Power supply in breaker	N/A	Optional	Standard	Standard
Additional Features				
Trip log (three events)	No	No	No	Yes
Electronic operations counter	No	No	No	Yes
Testing method ③	Test set	Test set	Test set	Integral and test set
Waveform capture	No	No	No	Yes
Arcflash Reduction Maintenance System Mode	No	No	Yes	Yes ④
Breaker health monitor	No	No	No	Yes
Programmable relay functions	No	No	No	Yes ①

Notes

① Over and undervoltage alarm or trip, over and underfrequency alarm or trip, voltage unbalance alarm or trip, reverse power trip and phase rotation alarm are included.

② Requires externally mounted MMINT or PMINT module.

③ Test set for secondary injection.

④ Contact Eaton for availability.

I_n = Rating plug rating.
I_r = LDPU setting.

i Trip units are only used on IEC breakers with earth fault.

Magnum Options and Accessories

Breaker-Mounted Options and Accessories

Magnum breakers are available with a comprehensive array of factory-installed breaker options to enable configured-to-order solutions for specified customer requirements. Field option kits are available to provide easy service, modification and customization of the breaker at the point of use.

- **Shunt Trip device (ST)**. Provides for remote electrically controlled breaker opening when energized by a rated voltage input
- **Spring Charge Motor (MOT)**. Charges the breaker closing springs automatically, facilitating remote or local closing. The motor assembly includes its own cut-off switch that changes state at the end of the charging cycle. This contact can be wired out for external indication
- **Spring Release device (SR)**. Provides for remote electrically controlled breaker closing when its coils are energized by a rated voltage input
- **Undervoltage Release (UVR)**. Trips the breaker when an existing voltage signal is lost or falls below an established threshold
- **Auxiliary Switch**. Up to 6a/6b auxiliary individual dedicated contacts are available for customer use to indicate if the breaker is in the OPEN or CLOSE position
- **Mechanical Trip Indicator Flag.** The red trip indicator flag pops out to provide local visual indication when the Digitrip RMS trip unit acts to trip the breaker on an overcurrent condition. Available in two options: an interlocked version that mechanically locks out the breaker until the indicator is manually reset and a non-interlocked version for indication only.
- **Bell Alarm/Overcurrent Trip Switch (OTS)**. Provides 2 Form C (changeover) contacts that change state when the Digitrip RMS trip unit acts to trip the breaker on an overcurrent condition. The contacts are available for external indication or customer use and are manually reset by the Mechanical Trip Indicator
- **Padlockable Pushbutton Cover**. Permits padlocking hinged cover plates to block access to the PUSH ON and PUSH OFF buttons on the breaker faceplate
- **Mechanical Operations Counter**. Records mechanical operations of the breaker over its installed life
- **Key Off Lock Provisions**. Enables mounting of a single cylinder Kirk®, Castell or Ronis key lock to lock the breaker in the OPEN position
- **Latch Check Switch**. Provides 1 Form C (changeover contact) that changes state when the breaker is ready to close. Can be wired to the Spring Release Device for fast transfer applications or wired for external ready-to-close indication

Arc Chutes are Easily Removable for Inspection and Access to Breaker Contacts

Heel-Toe Contact Design Provides Demonstrated Long Life and Includes Wear Indicator for Visual Inspection

Shunt Trip, Spring Release and Undervoltage Release Device Installed on Accessory Deck

Auxiliary Switches Come in Modular 2a/2b Contact Stages Providing up to 6a/6b Dedicated Contacts

Mechanical Trip Indicator With Bell Alarm (OTS) Switches Mounted

Magnum Breaker Control Device Application Guide—Vdc

Breaker Control Device Nominal Voltage		24 Vdc	32 Vdc	48 Vdc	60 Vdc	125 Vdc	250 Vdc
Shunt Trip (ST)—Trip Circuit							
Operational voltage range	70–110%	17–26 Vdc	—	34–53 Vdc	42–66 Vdc	77–138 Vdc	154–275 Vdc
Power consumption (inrush)	Required for 35 ms ①	250 W	—	250 W	250 W	450 W	450 W
Opening time	Seconds	35 ms	—	35 ms	35 ms	35 ms	35 ms
Spring Release (SR)—Close Circuit							
Operational voltage range	70–110%	17–26 Vdc	—	34–53 Vdc	42–66 Vdc	77–138 Vdc	154–275 Vdc
Power consumption (inrush)	Required for 200 ms	250 W	—	250 W	250 W	450 W	450 W
Closing time	Seconds	40 ms	—	40 ms	40 ms	40 ms	40 ms
Spring Charge Motor (MOT)							
Operational voltage range	85–110% voltage	20–26 Vdc	—	41–53 Vdc	51–66 Vdc	94–138 Vdc	187–225 Vdc
Amperes (running)	Running	12.0 A	—	5.0 A	4.0 A	2.0 A	1.0 A
Amperes (inrush)	% of running	300%	—	500%	500%	600%	600%
Power consumption	—	300 W	—	250 W	250 W	250 W	250 W
Charging time	Seconds	5 sec	—	5 sec	5 sec	5 sec	5 sec
Undervoltage Release (UVR)							
Operational voltage range	85–110% voltage	20–26 Vdc	27–35 Vdc	41–53 Vdc	51–66 Vdc	94–138 Vdc	187–275 Vdc
Dropout voltage range	30–60% voltage	7–14 Vdc	10–19 Vdc	14–29 Vdc	18–36 Vdc	33–75 Vdc	66–150 Vdc
Power consumption (inrush)	Required for 200 ms	250 W	275 W	275 W	275 W	450 W	450 W
Power consumption (continuous)	Required for 400 ms	18 W	15 W	18 W	18 W	10 W	10 W
Opening time	Seconds	70 ms	70 ms	70 ms	70 ms	70 ms	70 ms
Auxiliary Switches							
Minimum load contact rating	Inductive load	0.5 A	—	0.5 A	—	0.5 A	0.25 A

Magnum Breaker Control Device Application Guide—Vac

Breaker Control Device Nominal Voltage		120 Vac	240 Vac	415 Vac	480 Vac	600 Vac
Shunt Trip (ST)—Trip Circuit						
Operational voltage range	70 –110%	77–140 Vac	146–264 Vac	—	—	—
Power consumption (inrush)	Required for 35 ms	450 VA	450 VA	—	—	—
Opening time	Seconds	35 ms	35 ms	—	—	—
Spring Release (SR)—close circuit						
Operational voltage range	70–110%	77–140 Vac	146–264 Vac	—	—	—
Power consumption (inrush)	Required for 200 ms	450 VA	450 VA	—	—	—
Closing time	Seconds	40 ms	40 ms	—	—	—
Spring Charge Motor (MOT)						
Operational voltage range	85–110% voltage	93–140 Vdc	177–305 Vdc	—	—	—
Amperes (running)	Running	2.0 A	1.0 A	—	—	—
Amperes (inrush)	% of running	600%	600%	—	—	—
Power consumption	—	250 VA	250 VA	—	—	—
Charging time	Seconds	5 sec	5 sec	—	—	—
Undervoltage Release (UVR)						
Operational voltage range	85–110% voltage	94–140 Vac	177–264 Vac	323–457 Vac	408–528 Vac	510–660 Vac
Dropout voltage range	30–60% voltage	33–76 Vac	62–144 Vac	114–249 Vac	144–288 Vac	180–360 Vac
Power consumption (inrush)	Required for 200 ms	450 VA	400 VA	480 VA	400 VA	400 VA
Power consumption (continuous)	Required for 400 ms	10 VA	10 VA	10 VA	10 VA	10 VA
Opening time	Seconds	70 ms	70 ms	70 ms	70 ms	70 ms
Auxiliary Switches						
Minimum load contact rating	Inductive load	10 A	10 A	—	—	—

Note

① 100% duty shunt trips require power consumption (inrush) for 200 ms.

Wiring Diagrams

Typical Magnum Breaker Control Circuit

Legend:

LS	Limit Switch for Closing Spring
MOT	Motor for Spring Charging
ST	Shunt Trip ①
SR	Spring Release
UVR	Undervoltage Release
OTS	Overcurrent Trip Switch

Description of Operation:

1 — Motor is energized through LS contact.
2 — Motor runs and charges closing spring.
3 — When closing spring is fully charged, LS contacts change state.
4 — Close contacts energize SR coil.
5 — When breaker closes, "b" opens.
6 — LS contacts change state and motor recharges closing springs.

Notes

* Contacts shown for breaker open (not fully charged), not tripped.
– – – – Dotted line denotes Magnum Breaker.
① Not needed with 100% duty rated shunt.



Magnum DC (Direct Current) Low Voltage Switches

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	
Technical Data and Specifications	**V4-T3-34**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Magnum DC (Direct Current) Low Voltage Switches

Product Description

Eaton Magnum DC switches are a comprehensive offering of third-party and globally certified DC switches that are designed to provide excellent safety with a high level of performance that meets the demands of a global market.

Applications

The new line of Magnum DC switches covers a wide range industry applications.

- Utility companies incorporating DC facility power and control for emergency or redundant power
- Backup UPS power systems requiring means to disconnect the battery for isolation and maintenance
- SCR and drive isolation switches for maintenance and emergency disconnect

Features and Benefits

The new DC switch in the industry-proven Magnum platform provides DC technology in a common power breaker platform.

- The DC switch provides disconnect and switching to meet demanding industry standards:
  - UL1066—300 Vdc, 50 kA withstand and interruption, up to 3200 A continuous current
  - UL 489—600 Vdc, 50 kA withstand and interruption, up to 3200 A continuous current
  - IEC 60947-2—1000 Vdc, 25 kA interruption and 65 kA withstand, up to 3200 A
- Common accessories with the Magnum AC line of power circuit breakers reduces inventory and integration time
- Fixed and drawout versions address important design criteria, balancing cost, size and serviceability
- Internationally approved factory-installed and field-installable accessories identical to the Magnum air circuit breaker offering

Standards and Certifications

UL and ANSI Test Certifications

Magnum DC switches meet or exceed the applicable ANSI, NEMA, UL and CSA standards, including:

- ANSI C37.14 (Low Voltage DC Power Circuit Breakers Used in Enclosures)
- ANSI C37.16 (Preferred Ratings, Related Requirements, and Application Recommendations for Low Voltage Power Circuit Breakers and AC and DC Power Circuit Breakers)
- ANSI C37.17 (Trip Devices for AC and General Purpose DC Low Voltage Power Circuit Breakers)
- UL 1066 (Standard for Low Voltage AC and DC Power Circuit Breakers Used in Enclosures)
- UL 489 Molded Case Switches

IEC Test Certification

Magnum Air Circuit Breakers meet or exceed the applicable IEC standards

- EN/IEC 60947-2

Approvals and Marks

- UL listed: Magnum DS Breaker UL File No. E52096 and Cassette UL File No. E204565
- ABS (American Bureau of Shipping) Type Approval
- CE
- CCC (Certificate for China Compulsory Product Certification) to GB14048.2-2001
- Det Norske Veritas (DNV)
- Lloyds of London
- South African Bureau of Standards (SABS)
- For a complete and comprehensive listing of all low voltage power breakers, please visit www.eaton.com

Product Selection

Contact Eaton for pricing.

Technical Data and Specifications

Ratings for Magnum DC Switches

Catalog Type/standard	Frame Type	Number of Poles	Frame Ampere Rating	DC Voltage/ Interrupt Rating/ Withstand Rating	Load Switching	For Use in Grounded Systems	Connection Type	Fixed/ Drawout	Certification
ANSI/UL 1066 ratings at 300 Vdc									
DAS	Standard	3	1600	300 V / 50 kA / 50 kA	Yes	Yes	Two-pole in series	Drawout	UL 1066
DAS	Standard	3	2000	300 V / 50 kA / 50 kA	Yes	Yes	Two-pole in series	Drawout	UL 1066
DAS	Standard	3	3200	300 V / 50 kA / 50 kA	Yes	Yes	Two-pole in series	Drawout	UL 1066
UL 489 ratings at 600 Vdc									
DBS	Standard	3	3200	600 V / 50 kA / 50 kA	Yes	Yes	Three-pole in series	Both	UL 489
IEC ratings at 1000 Vdc ①									
DEM/DGM	Narrow	3	800	1000 V / 25 kA / 65 kA	Yes	No/yes ①	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Narrow	3	1000	1000 V / 25 kA / 65 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Narrow	3	1250	1000 V / 25 kA / 65 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Narrow	3	1600	1000 V / 25 kA / 65 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Narrow	3	2000	1000 V / 25 kA / 65 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEK/DGK	Standard	3	2500	1000 V / 25 kA / 85 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEK/DGK	Standard	3	3200	1000 V / 25 kA / 85 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Double narrow	6	4000	1000 V / 25 kA / 100 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEM/DGM	Double narrow	6	5000	1000 V / 25 kA / 100 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEK/DGK	Double standard	6	4000	1000 V / 25 kA / 100 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2
DEK/DGK	Double standard	6	5000	1000 V / 25 kA / 100 kA	Yes	No/yes	Three-pole in series	Both	IEC 60947-2

Note

① DE is for use in ungrounded applications; DG is for use in grounded applications.

Series NRX Low Voltage Power Circuit Breaker with Power Xpert Release Trip Unit (PXR)

Series NRX with PXR NF Drawout Breaker

Series NRX with PXR RF Fixed Breaker

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	
Catalog Number Selection	**V4-T3-38**
Technical Data and Specifications	**V4-T3-42**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	**V4-T3-55**

Series NRX Low Voltage Power Circuit Breakers with PXR

Product Description

Series NRX is a low voltage power circuit breaker suitable for UL 1558, UL 891, and IEC switchgear and switchboards. The compact size and weight of three-pole drawout with cassette Series NRX, see **Pages V4-T3-39** and **V4-T3-41**, allows for a 24.00 (609.6 mm) switchgear enclosure. Series NRX with Power Release Xpert (PXR) trip unit is available with a variety of cable and bus connection options: rear fixed, front fixed, fixed hybrid and drawout.

The breaker ratings are:

NF Frame

- 800–1200 A for UL 489
- 630–1600 A IEC 60947-2

RF Frame

- 800–3000 A for UL 489
- 800–4000 A for IEC 60947-2

Application Description

The compact sizes of the two Series NRX circuit breakers, NF and RF frames, help reduce non-revenue generating floor space, and the modular design and common accessories allow for easy panel and switchboard integration. The Series NRX circuit breakers combine high interruption and short time withstand ratings with easy to integrate communications. NF Frame is rated for 800 A (UL 1066), 800 A and 1200 A (UL 489) and 630–1600 A (IEC 60947-2) with an interrupting capacity of 65 kA with short time withstand at 42 kA at the 440/480 Vac level. RF Frame is rated for 800–3000 A (UL 489) and 800–4000 A (IEC 60947-2) with an interrupting capacity of 100 kA with short time withstand at 65 kA (or 85 kA for IEC 60947-2) at the 440/480 Vac level.

The Series NRX circuit breaker provides all the capabilities of a power circuit breaker in the compact size of a molded case breaker. It offers you the same protection and performance —along with increased flexibility—at half the size of a typical power circuit breaker.

Eaton's new PXR electronic trip units provide advanced metering, communication and diagnostic features with an easy-to-use interface. The Power Xpert® Protection Manager (PXPM) software for the PXR trip units can provide and perform secondary injection and test reporting through a PC to simplify testing, serviceability and customization.

Features, Benefits and Functions

Series NRX utilizes several innovative technologies:

- Rogowski coil—does not saturate like iron core sensors, and one sensor accommodates 200–1600 ampere range for NF and 800–4000 for RF. You never have to change a sensor and CTs are not required
- Tension clamp secondary terminals—10 A continuous rating at 600 V meets UL/CSA/RoHS and UL-94 V0. Mounted directly to fixed breaker or drawout cassette, they reduce wiring throughout enclosure and provide clean, organized wiring schemes
- A Modbus® communication port is standard in the PXR 25 trip units and is available as an option on PXR 20 trip units. This native Modbus RTU capability gives access to breaker status and metering information. Additional PCAM, MCAM or ECAM modules can be installed externally for PXR to expand the communication capability and simplify integration into existing electrical system design and protocols
- "Direct Drive" mechanism—symmetrically loaded forces of the two-staged stored energy mechanism improves robustness, reliability, and achieves improved breaker life ratings
- Fold-up cassette—with this simple design, all items in a cassette are replaceable without removing the cassette from the cell
- "Arc chute" design
- Breaker-mounted racking or levering-in device—Racking device is mounted on the breaker, decreasing the width of the cassette, because the cassette is not burdened with the cost or parts of the lev-in
- Plug-n-Play accessories—No special tools needed. Accessory comes with plug and wires ready to install
- Arcflash Reduction Maintenance System—Eaton's patented technology provides maintenance staff with improved safety of downstream maintenance locations using a simple and reliable method to reduce fault clearing times and energy during an arc flash event (radiation, sound, pressure, temperature). Arcflash Reduction Maintenance System uses a separate analog trip circuit, providing faster signal processing and interruption times than the standard (digital) "instantaneous" protection. The Arcflash Reduction Maintenance System function is activated either directly on the circuit breaker through a local switch or remotely through communications or a digital input

Note: UL 489: For $I_n \leq 2500$ A, mechanical ops =2500. For $I_n < 2500$, mechanical ops = 1500. For $I_n \leq 2500$ A, mechanical ops = 3000. For $I_n > 2500$, mechanical ops = 2000.

Standards and Certifications

- UL 489 (molded case circuit breakers, molded case switches and circuit breaker enclosures)
- IEC 60947-1 (low voltage switchgear and controlgear —Part 1 general rules)
- IEC 60947-2 (low voltage switchgear and controlgear —Part 2 circuit breakers)
- CSA 22.2 (molded case circuit breakers, molded case switches and circuit breaker enclosures)
- UL 891 (deadfront switchboard)
- UL 1558 (metal-enclosed low voltage power circuit breaker switchgear)

Reference Information—Series NRX with PXR Publications

List of Instruction Leaflets and Manuals

Description	Publication Number	Frame Number
NF Frames		
Series NRX—Installation Instructions for Operation Counter	IL01301011E	NF
Series NRX—Installation Instructions for Drawout Cassette IP20 Safety Shutters	IL01301013E	NF
Series NRX—Installation Instructions for Fixed Breaker Arc Hood	IL01301014E	NF
Series NRX—Installation Instructions for Drawout Breaker Primary Adapters	IL01301016E	NF
Series NRX—Installation Instructions for Breaker and Cassette Interphase Barriers	IL01301021E	NF
Series NRX—Installation Instructions for Pushbutton Cover Kit	IL01301041E	NF
Series NRX—Installation Instructions for Drawout Circuit Breaker 2-Way Cable Interlock Kit	IL01301069E	NF
Series NRX—Installation Instructions for Drawout Circuit Breaker 3-Way Cable Interlock Kit	IL01301070E	NF
Series NRX—Installation Instructions for Fixed Circuit Breaker 2-Way Cable Interlock Kit	IL01301071E	NF
Series NRX—Installation Instructions for Fixed Circuit Breaker 3-Way Cable Interlock Kit	IL01301072E	NF
Series NRX—Installation Instructions for Cassette Door Interlock	IL01301073E	NF
Series NRX with PXR—Instructions for Neutral Current Sensor—Type NF	IL0131090EN	NF
Series NRX with PXR—Instructions for Cassette Cell Switch—Type NF	IL0131097EN	NF
Series NRX—Fixed Breaker Rear Connect and Front Connect Configurations	IL0131123EN	NF
Series NRX with PXR, Type NF low voltage power (air) circuit breakers instruction manual	MN013001EN	NF
Series NRX—Installation Instructions for Pop-Out Mechanical Trip Indicator	IL01301019E	NF

List of Instruction Leaflets and Manuals, continued

Description	Publication Number	Frame Number
RF Frames		
Series NRX—Installation Instructions for Drawout Cassette IP20 Safety Shutters	IL01301044E	RF
Series NRX—Installation Instructions for Breaker and Cassette Interphase Barrier	IL01301048E	RF
Series NRX—Installation Instructions for Rear Primary Adapters	IL01301053E	RF
Series NRX—Installation Instructions for Operation Counter	IL01301055E	RF
Series NRX—Installation Instructions for Front Connect Adapters	IL01301056E	RF
Series NRX—Installation Instructions for Pop-Out Mechanical Trip Indicator	IL01301058E	RF
Series NRX—Installation Instructions for Drawout Circuit Breaker 2-Way Cable Interlock Kit	IL01301059E	RF
Series NRX—Installation Instructions for Drawout Circuit Breaker 3-Way Cable Interlock Kit	IL01301060E	RF
Series NRX—Installation Instructions for Fixed Circuit Breaker 2-Way Cable Interlock Kit	IL01301061E	RF
Series NRX—Installation Instructions for Fixed Circuit Breaker 3-Way Cable Interlock Kit	IL01301062E	RF
Series NRX—Installation Instructions for Lev-in Key Interlocks	IL01301063E	RF
Series NRX—Installation Instructions for Pushbutton Cover Kit	IL01301065E	RF
Series NRX—Installation Instructions for Cassette Door Interlock	IL01301066E	RF
Series NRX with PXR—Instructions for Neutral Current Sensor—Type RF	IL0131094EN	RF
Series NRX with PXR—Instructions for Cassette Cell Switch—Type RF	IL0131095EN	RF
Series NRX with PXR, Type RF low voltage power (air) circuit breakers instruction manual	MN013002EN	RF
NF and RF Frames		
Series NRX NF & RF Circuit Breakers with PXR 20/25 Trip Units - Time Current Curves	AD013001EN	NF and RF
Series NRX Drawout Circuit Breaker and Cassette Rejection Interlocks	IL01301006E	NF and RF
Series NRX—Installation Instructions for Fixed and Drawout Breaker Door Escutcheon	IL01301012E	NF and RF
Series NRX—Installation Instructions for IP55 Dust and Water-Resistant Cover	IL01301038E	NF and RF
Series NRX—Installation Instructions for Kirk Key Interlock Kit	IL01301039E	NF and RF
Series NRX—Installation Instructions for Ronis Key Lock Kit	IL01301040E	NF and RF
Series NRX—Installation Instructions for CES Key Lock Kit	IL01301049E	NF and RF
Series NRX—Installation Instructions for Castell Key Lock Kit	IL01301050E	NF and RF
Series NRX with PXR—Instructions for PT Module	IL01301074E	NF and RF
Series NRX with PXR—Instructions for Undervoltage Release, Shunt Trip, and Overcurrent Trip Switch	IL0131087EN	NF and RF
Series NRX with PXR—Instructions for Spring Release, Latch Check Switch, and Motor Operator	IL0131088EN	NF and RF
Series NRX with PXR—Instructions for Source Ground and Zero Sequence Ground Sensor	IL0131089EN	NF and RF
Series NRX with PXR—Instructions for Modbus Communications Adapter Module (MCAM)	IL0131091EN	NF and RF
Series NRX with PXR—Instructions for PROFIBUS DP Communications Adaptor Module (PCAM)	IL0131092EN	NF and RF
Series NRX with PXR—Instructions for Secondary Terminal Blocks	IL0131093EN	NF and RF
Series NRX with PXR—Instructions for Auxiliary Switch	IL0131096EN	NF and RF
Series NRX with PXR—Instructions for INCOM Communications Adapter Module	IL0131124EN	NF and RF
Series NRX with PXR—Installation Instructions for Ethernet Communications Adapter Module	IL0131125EN	NF and RF
PXR 20/25 Trip Unit for Series NRX Screen Navigation Guide	IL0131128EN	NF and RF
Time Delay Undervoltage Module for use with Undervoltage Release in Eaton Circuit Breakers	IL5721B33	NF and RF
PXR 20/25 Trip Unit for Series NRX User Manual	MN013003EN	NF and RF
Series NRX with PXR Circuit Breaker Wiring Diagrams	TD013001EN	NF and RF

Catalog Number Selection

Series NRX with Power Xpert Release NF Frame Circuit Breaker (exclusionary rules apply)

N G S6 08 3 W 2A 8 A B A N 4 X N D X

Breaker Frame Size
- **N** = NF-frame for UL 489 or IEC

Standard, Mechanism, Device
- **G** = IEC 60947-2, stored energy, air breaker
- **Y** = UL 489, stored energy, insulated case breaker

Fault Current Rating
- **R4** = 42 kA at 480 Vac (UL 489 only)
- **R5** = 50 kA at 480 Vac (UL 489 only)
- **R6** = 65 kA at 480 Vac (UL 489 only)
- **S4** = 42 kA at 480 Vac (30 cycle, UL 489) or 415 Vac IEC
- **S5** = 50 kA at 480 Vac (30 cycle, UL 489) or 415 Vac IEC
- **S6** = 65 kA at 480 Vac (30 cycle, UL 489 only), 66 kA at 415 Vac IEC

Frame Rating (Amperes)
- **07** = 630 (IEC only)
- **08** = 800
- **10** = 1000 (IEC only)
- **12** = 1200 (UL only)
- **13** = 1250 (IEC only)
- **16** = 1600 (IEC only)

Poles, Phasing
- **3** = Three-pole, ABC
- **4** = Four-pole, NABC

Mounting Configuration
- **W** = Drawout
- **B** = Fixed mount rear connected with side mounting brackets
- **F** = Front connected, fixed mount, for bus or cable connections with side mounting brackets①
- **H** = Fixed hybrid breaker, top rear connect and bottom front connect ②
- **J** = Fixed hybrid breaker, top front connect and bottom rear connect ②

Trip Unit, Power Supply
- **SW** = Non-automatic switch, available only for fault current rating configuration S4
- **2A** = PXR20 LSI
- **2B** = PXR20 LSI with Modbus
- **2H** = PXR20 LSI with Modbus and Arcflash Reduction Maintenance System
- **2K** = PXR20 LSI with Arcflash Reduction Maintenance System
- **2C** = PXR20 LSIG
- **2D** = PXR20 LSIG with Modbus
- **2E** = PXR20 LSIG with Arcflash Reduction Maintenance System
- **2F** = PXR20 LSIG with Modbus and Arcflash Reduction Maintenance System
- **2P** = PXR25 LSI with Modbus
- **2Q** = PXR25 LSI with Modbus and Arcflash Reduction Maintenance System
- **2R** = PXR25 LSIG with Modbus
- **2S** = PXR25 LSIG with Modbus and Arcflash Reduction Maintenance System

Continuous Rating (I_n in Amperes)
- **0** = Non-auto switch
- **1** = 200
- **2** = 250
- **3** = 300
- **4** = 400
- **5** = 500
- **6** = 600
- **7** = 630 (IEC only)
- **8** = 800
- **A** = 1000 (IEC only)
- **B** = 1200 (UL only)
- **C** = 1250 (IEC only)
- **D** = 1600 (IEC only)

Shunt Trip
- **N** = No shunt trip
- **A** = 110–127 Vac/Vdc
- **R** = 208–240 Vac/Vdc
- **L** = 24 Vdc
- **H** = 48 Vdc
- **S** = 60 Vdc

Motor Operator
- **M** = Manually operated
- **B** = 110–125 Vac/Vdc
- **W** = 110–125 Vdc
- **T** = 208–250 Vac/Vdc
- **P** = 220–250 Vdc
- **L** = 24 Vdc
- **H** = 48 Vdc
- **S** = 60 Vdc

Spring Release, Latch Check Switch
- **N** = No spring release, no LCS
- **A** = 110–127 Vac/Vdc, no LCS
- **B** = 110–127 Vac/Vdc, spring release LCS
- **C** = 110–127 Vac/Vdc, LCS wired external
- **R** = 208–250 Vac/Vdc, no LCS
- **S** = 208–250 Vac/Vdc, spring release LCS
- **T** = 208–250 Vac/Vdc, LCS wired external
- **L** = 24 Vdc, no LCS
- **P** = 24 Vdc, spring release LCS
- **Q** = 24 Vdc, LCS wired external
- **H** = 48 Vdc, no LCS
- **J** = 48 Vdc, spring release LCS
- **K** = 48 Vdc, LCS wired external
- **1** = 60 Vdc, no LCS
- **2** = 60 Vdc, spring release LCS
- **3** = 60 Vdc, LCS wired external

Notes

① Four-pole cable kit only available up to 50 kA, 65 kA cable kit not available at this time.

② UL 489 three-pole only.

Series NRX with Power Xpert Release NF Frame Circuit Breaker (exclusionary rules apply), continued

N G S6 08 3 W 2A 8 A B A N 4 X N D X

UVR, Second Shunt Trip

- **N** = None
- **A** = 110–125 Vac/Vdc UVR
- **R** = 220–250 Vac/Vdc UVR
- **L** = 24 Vdc UVR
- **H** = 48 Vdc UVR
- **S** = 60 Vdc UVR
- **1** = 110–127 Vac/Vdc second shunt trip
- **2** = 208–240 Vac/Vdc second shunt trip
- **4** = 24 Vdc second shunt trip
- **8** = 48 Vdc second shunt trip
- **9** = 60 Vdc second shunt trip

	Trip Indicator and Bell Alarm ①	OTS	Secondary Terminal Blocks	Remote Reset
N	None	None	Per breaker options	None
X	Trip indicator	None	Per breaker options	None
Z	Trip indicator	2 Form C	Per breaker options	None
M	Interlock trip indicator	None	Per breaker options	None
Y	Interlock trip indicator	2 Form C	Per breaker options	None
1	None	None	Full complement	None
2	Trip indicator	None	Full complement	None
3	Trip indicator	2 Form C	Full complement	None
4	Interlock trip indicator	None	Full complement	None
5	Interlock trip indicator	2 Form C	Full complement	None

Drawout Breaker Shipping, Fixed Breaker Terminals (Door frame kit ships as standard unless noted otherwise)

- **D** = Drawout breaker shipping alone, without door frame kit
- **C** = Drawout breaker shipping in cassette, no shutters, no terminals
- **1** = Drawout breaker shipping in cassette, no shutters, short vertical/horizontal
- **2** = Drawout breaker shipping in cassette, no shutters, long vertical/horizontal
- **4** = Drawout breaker shipping in cassette, with shutters, short vertical/horizontal
- **5** = Drawout breaker shipping in cassette, with shutters, long vertical/horizontal
- **9** = Drawout breaker shipping in cassette, with shutters, no terminals
- **K** = Rear connect, fixed breaker, no terminal adapters
- **F** = Fixed breaker, rear connect, with mounting feet and short terminal adapters
- **H** = Fixed breaker, rear connect, with mounting feet and long terminal adapters
- **J** = Front connect, fixed breaker, with no terminal adapters
- **Q** = Fixed hybrid, no rear terminals, TA1200NB1M front cable terminals
- **T** = Fixed hybrid, no rear terminals, TA1201NB1M front cable terminals

Auxiliary Switches, Label Language

- **E** = No auxiliary switches, English
- **2** = 2 Form C, English
- **4** = 4 Form C, English

	Pushbutton Padlock Cover	Safe OFF Feature	Operations Counter
N	No	None	No
A	No	—	Provided
B	Yes (plastic/plastic)	—	No
J	Yes (plastic/plastic)	—	Provided
K	Yes (metal/metal)	—	No
L	Yes (metal/metal)	—	Provided
1	Yes (metal/metal)	Yes	No
2	Yes (metal/metal)	Yes	Provided

Series NRX with Power Xpert Release NF Frame Cassette

NY 12 3 F A B N S N N N C

Cassette Family and Breaker Frame

- **NY** = UL 489 NF Frame
- **NG** = IEC NF Frame

Continuous Ampere Range

- **12** = 800–1200 (UL 489)
- **16** = 630–1600 (IEC)

Poles and Phasing (Facing front of breaker)

- **3** = Three-pole ABC
- **4** = Four-pole NABC

Load Terminal Connections

- **A** = With vertical/horizontal bus adapter kit (long style)
- **F** = With flat tapped pads only
- **G** = With vertical/horizontal bus adapter kit (short style)

Arc Hood

- **A** = Arc hood installed (default)

Door Frame Gasket and Rejection Kits

- **B** = Door kit included (default), with rejection kit

Cell Switch Options

- **N** = Not included

Shutters

- **N** = Not included (default)
- **S** = Included

Second Contact Terminals Installed

- **N** = None
- **B** = Breaker defined, when breaker ships in cassette
- **F** = Full complement

Future

- **N** = None

Future

- **N** = None

Cassette Shipping

- **C** = Cassette only
- **B** = Breaker shipped in cassette

Note

① Two Form C contacts except on NF with Power Xpert Release and OTS and RRTI, where only one Form C OTS contact will be provided.

Series NRX with Power Xpert Release RF Frame Circuit Breaker (exclusionary rules apply)

R G S6 08 3 W 2A 8 A B A N 4 X N D X

Breaker Frame Size
- **R** = RF frame for UL 489 or IEC

Standard, Mechanism, Device
- **G** = IEC 60947-2, stored energy, air breaker
- **Y** = UL 489, stored energy, insulated case breaker

Fault Current Rating
- **R6** = 65 kA at 480 Vac (UL 489 only)
- **R8** = 85 kA at 480 Vac (UL 489 only)
- **RC** = 100 kA at 480 Vac (UL 489 only)
- **S5** = 55 kA at 415 Vac (IEC only)
- **S6** = 65 kA at 480 Vac (30 cycle, UL 489 only), 66 kA at 415 Vac IEC
- **S8** = 85 kA at 480 Vac (30 cycle, UL 489 only)
- **SC** = 100 kA at 480 Vac (30 cycle, UL 489 only), 105 kA at 415 Vac IEC

Frame Rating (Amperes)

08 = 800	**20** = 2000
10 = 1000 (IEC only)	**25** = 2500
12 = 1200 (UL only)	**30** = 3000 (UL only)
13 = 1250 (IEC only)	**32** = 3200 (IEC only)
16 = 1600	**40** = 4000 (IEC only)

Poles, Phasing
- **3** = Three-pole, ABC
- **4** = Four-pole, NABC

Mounting Configuration
- **W** = Drawout with universal pads
- **B** = Fixed mount rear connected with side mounting brackets

Trip Unit, Power Supply
- **SW** = Non-automatic switch, available only for fault current rating configurations S6 and S8
- **2A** = PXR20 LSI
- **2B** = PXR20 LSI with Modbus
- **2H** = PXR20 LSI with Modbus and Arcflash Reduction Maintenance System
- **2K** = PXR20 LSI with Arcflash Reduction Maintenance System
- **2C** = PXR20 LSIG
- **2D** = PXR20 LSIG with Modbus
- **2E** = PXR20 LSIG with Arcflash Reduction Maintenance System
- **2F** = PXR20 LSIG with Modbus and Arcflash Reduction Maintenance System
- **2P** = PXR25 LSI with Modbus
- **2Q** = PXR25 LSI with Modbus and Arcflash Reduction Maintenance System
- **2R** = PXR25 LSIG with Modbus
- **2S** = PXR25 LSIG with Modbus and Arcflash Reduction Maintenance System

Continuous Rating (I_n in Amperes)
- **0** = Non-auto switch
- **8** = 800
- **A** = 1000 (IEC only)
- **B** = 1200 (UL only)
- **C** = 1250 (IEC only)
- **D** = 1600
- **M** = 2000
- **N** = 2500
- **P** = 3000 (UL only)
- **Q** = 3200 (IEC only)
- **R** = 4000 (IEC only)

Shunt Trip
- **N** = No shunt trip
- **A** = 110–127 Vac/Vdc
- **R** = 208–240 Vac/Vdc
- **L** = 24 Vdc
- **H** = 48 Vdc
- **S** = 60 Vdc

Motor Operator
- **M** = Manually operated
- **B** = 110–125 Vac
- **T** = 208–250 Vac
- **L** = 24 Vdc
- **H** = 48 Vdc
- **S** = 60 Vdc

Spring Release, Latch Check Switch
- **N** = No spring release, no LCS
- **A** = 110–127 Vac/Vdc, no LCS
- **B** = 110–127 Vac/Vdc, spring release LCS
- **C** = 110–127 Vac/Vdc, LCS wired external
- **R** = 208–250 Vac/Vdc, no LCS
- **S** = 208–250 Vac/Vdc, spring release LCS
- **T** = 208–250 Vac/Vdc, LCS wired external
- **L** = 24 Vdc, no LCS
- **P** = 24 Vdc, spring release LCS
- **Q** = 24 Vdc, LCS wired external
- **H** = 48 Vdc, no LCS
- **J** = 48 Vdc, spring release LCS
- **K** = 48 Vdc, LCS wired external
- **1** = 60 Vdc, no LCS
- **2** = 60 Vdc, spring release LCS
- **3** = 60 Vdc, LCS wired external

Series NRX with Power Xpert Release RF Frame Circuit Breaker (exclusionary rules apply), continued

R G S6 08 3 W 2A 8 A B A N 4 X N D X

UVR, Second Shunt Trip

- **N** = None
- **A** = 110–125 Vac/Vdc UVR
- **R** = 220–250 Vac/Vdc UVR
- **L** = 24 Vdc UVR
- **H** = 48 Vdc UVR
- **S** = 60 Vdc UVR
- **1** = 110–127 Vac/Vdc second shunt trip
- **2** = 208–240 Vac/Vdc second shunt trip
- **4** = 24 Vdc second shunt trip
- **8** = 48 Vdc second shunt trip
- **9** = 60 Vdc second shunt trip

Auxiliary Switches, Label Language

- **E** = No auxiliary switches, English
- **2** = 2 Form C, English
- **4** = 4 Form C, English
- **6** = 6 Form C, English
- **8** = 8 Form C, English
- **A** = 10 Form C, English
- **W** = 12 Form C, English

	Trip Indicator and Bell Alarm	OTS	Secondary Terminal Blocks	Remote Reset
N	None	None	Per breaker options	None
X	Trip indicator	None	Per breaker options	None
Z	Trip indicator	2 Form C	Per breaker options	None
M	Interlock trip indicator	None	Per breaker options	None
A	Interlock trip indicator	None	Per breaker options	24 Vdc RR
6	Interlock trip indicator	None	Per breaker options	48 Vdc RR
7	Interlock trip indicator	None	Per breaker options	60 Vdc RR
B	Interlock trip indicator	None	Per breaker options	120 Vdc RR
C	Interlock trip indicator	None	Per breaker options	240 Vdc RR
Y	Interlock trip indicator	2 Form C	Per breaker options	None
D	Interlock trip indicator	2 Form C	Per breaker options	24 Vdc RR
8	Interlock trip indicator	2 Form C	Per breaker options	48 Vdc RR
9	Interlock trip indicator	2 Form C	Per breaker options	60 Vdc RR
E	Interlock trip indicator	2 Form C	Per breaker options	120 Vdc RR
F	Interlock trip indicator	2 Form C	Per breaker options	240 Vdc RR
1	None	None	Full complement	None
2	Trip indicator	None	Full complement	None
3	Trip indicator	2 Form C	Full complement	None
4	Interlock trip indicator	None	Full complement	None
J	Interlock trip indicator	None	Full complement	24 Vdc RR
G	Interlock trip indicator	None	Full complement	48 Vdc RR
H	Interlock trip indicator	None	Full complement	60 Vdc RR
K	Interlock trip indicator	None	Full complement	120 Vdc RR
L	Interlock trip indicator	None	Full complement	240 Vdc RR
5	Interlock trip indicator	2 Form C	Full complement	None
R	Interlock trip indicator	2 Form C	Full complement	24 Vdc RR
U	Interlock trip indicator	2 Form C	Full complement	48 Vdc RR
V	Interlock trip indicator	2 Form C	Full complement	60 Vdc RR
S	Interlock trip indicator	2 Form C	Full complement	120 Vdc RR
T	Interlock trip indicator	2 Form C	Full complement	240 Vdc RR

Options

- **X** = Default
- **W** = Low temperature applications (–57 °C)

Drawout Breaker Shipping, Fixed Breaker Terminals (Door frame kit ships as standard unless noted otherwise)

- **D** = Drawout breaker shipping alone, without door frame kit
- **C** = Drawout breaker shipping in cassette, no shutters, no terminals
- **1** = Drawout breaker shipping in cassette, no shutters, vertical adapters
- **2** = Drawout breaker shipping in cassette, no shutters, horizontal adapters
- **4** = Drawout breaker shipping in cassette, with shutters, vertical adapters
- **5** = Drawout breaker shipping in cassette, with shutters, horizontal mounting
- **9** = Drawout breaker shipping in cassette, with shutters, no terminals
- **K** = Rear connect, fixed breaker, no terminal adapters
- **F** = Fixed breaker, rear connect with vertical adapters
- **H** = Fixed breaker, rear connect with horizontal adapters

	Pushbutton Padlock Cover	Safe OFF Feature	Operations Counter
N	No	None	No
A	No	—	Provided
B	Yes (plastic/plastic)	—	No
J	Yes (plastic/plastic)	—	Provided
K	Yes (metal/metal)	—	No
L	Yes (metal/metal)	—	Provided
1	Yes (metal/metal)	Yes	No
2	Yes (metal/metal)	Yes	Provided

Series NRX with Power Xpert Release RF Frame Cassette

RY 12 3 F A B N S N N N C

Cassette Family and Breaker Frame

- **RY** = UL 489 NF Frame
- **RG** = IEC NF Frame

Continuous Ampere Range

- **30** = 3000 A (UL only)
- **40** = 3200–4000 A (IEC only)

Poles and Phasing (Facing front of breaker)

- **3** = Three-pole ABC
- **4** = Four-pole NABC

Load Terminal Connections

- **F** = With flat tapped pads only (no terminals)
- **G** = With vertical/horizontal bus adapter kit (short style)
- **A** = With vertical/horizontal bus adapter kit (long style)

Arc Hood

- **A** = Arc hood installed (default)

Door Frame Gasket and Rejection Kits

- **B** = Door kit included (default), with rejection kit

Cell Switch Options (Available on breaker + cassette or cassette only)

- **N** = Not included
- **3** = Cell switch assembly with 3 Form C contacts

Shutters

- **N** = Not included (default)
- **S** = Included

Second Contact Terminals Installed

- **N** = None
- **B** = Breaker defined, when breaker ships in cassette
- **F** = Full complement

Future

- **N** = None

Future

- **N** = None

Cassette Shipping

- **C** = Cassette only
- **B** = Breaker shipped in cassette

Technical Data and Specifications

UL 489 Ratings

Frame Amperes	Breaker Type Catalog Number	Frame Type	1 rms Symmetrical Current Ratings kA 50/60 Hz Interrupting at 240 Vac	Interrupting at 480 Vac	Interrupting at 600 Vac	30 Cycle Short-Time Withstand Rating ①	Instantaneous Override (Equivalent Symmetrical rms, kA) ②	Poles Available	Available Trip Rating (Establishes Breaker I_n Rating) ③
NF Frame—UL 489									
800	NYR4-08	NF-R	50	42	42	16 x I_n	16 x I_n	3, 4	200, 250, 300, 400, 500, 600, 800
	NYR5-08	NF-R	65	50	42	16 x I_n	16 x I_n	3, 4	
	NYR6-08	NF-R	85	65	42	16 x I_n	16 x I_n	3, 4	
1200	NYR4-12	NF-R	50	42	42	16 x I_n	16 x I_n	3, 4	200, 250, 300, 400, 500, 600, 800, 1200
	NYR5-12	NF-R	65	50	42	16 x I_n	16 x I_n	3, 4	
	NYR6-12	NF-R	85	65	42	16 x I_n	16 x I_n	3, 4	
NF Frame—UL 489 with high short-time (30 cycle) withstand capabilities									
800	NYS4-08	NF-S	50	42	42	42	42	3, 4	200, 250, 300, 400, 500, 600, 800
	NYS5-08	NF-S	65	50	42	42	42	3, 4	
	NYS6-08	NF-S	85	65	42	42	42	3, 4	
1200	NYS4-12	NF-S	50	42	42	42	42	3, 4	200, 250, 300, 400, 500, 600, 800, 1200
	NYS5-12	NF-S	65	50	42	42	42	3, 4	
	NYS6-12	NF-S	85	65	42	42	42	3, 4	
RF Frame—UL 489									
800	RYR5-08	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800
	RYR8-08	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-08	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
1200	RYR5-12	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800, 1200
	RYR8-12	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-12	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
1600	RYR5-16	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800, 1200, 1600
	RYR8-16	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-16	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
2000	RYR5-20	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800, 1200, 1600, 2000
	RYR8-20	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-20	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
2500	RYR5-25	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800, 1200, 1600, 2000, 2500
	RYR8-25	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-25	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
3000	RYR5-30	RF–R	65	65	—	16 x I_n	16 x I_n	3, 4	800, 1200, 1600, 2000, 2500, 3000
	RYR8-30	RF–R	85	85	—	16 x I_n	16 x I_n	3, 4	
	RYRC-30	RF–R	100	100	—	16 x I_n	16 x I_n	3, 4	
RF Frame—UL 489 with high short-time (30 cycle) withstand capabilities									
800	RYS6-08	RF-S	65	65	—	65	—	3, 4	800
	RYS8-08	RF-S	85	85	—	65	65	3, 4	
	RYSC-08	RF-S	100	100	—	65	65	3, 4	
1200	RYS6-12	RF-S	65	65	—	65	—	3, 4	800, 1200
	RYS8-12	RF-S	85	85	—	65	65	3, 4	
	RYSC-12	RF-S	100	100	—	65	65	3, 4	
1600	RYS6-16	RF-S	65	65	—	65	—	3, 4	800, 1200, 1600
	RYS8-16	RF-S	85	85	—	65	65	3, 4	
	RYSC-16	RF-S	100	100	—	65	65	3, 4	
2000	RYS6-20	RF-S	65	65	—	65	—	3, 4	800, 1200, 1600, 2000
	RYS8-20	RF-S	85	85	—	65	65	3, 4	
	RYSC-20	RF-S	100	100	—	65	65	3, 4	
2500	RYS6-25	RF-S	65	65	—	65	—	3, 4	800, 1200, 1600, 2000, 2500
	RYS8-25	RF-S	85	85	—	65	65	3, 4	
	RYSC-25	RF-S	100	100	—	65	65	3, 4	
3000	RYS6-30	RF-S	65	65	—	65	—	3, 4	800, 1200, 1600, 2000, 2500, 3000
	RYS8-30	RF-S	85	85	—	65	65	3, 4	
	RYSC-30	RF-S	100	100	—	65	65	3, 4	

Notes

① UL 489 does not require a short-time withstand rating for breakers. The UL 489 Series NRX breakers have instantaneous override fixed at 22.5 x I_n (asymmetrical peak value). An equivalent symmetrical rms value would roughly equate to 16 x I_n.

② A 30-cycle withstand option is available for Series NRX breakers to provide better selectivity.

③ No change of hardware is required, trip rating can be programmed using I_n Programming Tool Kit.

Mounting and Load Connection Configurations—NF Frame

Breaker Type	Breaker Mechanism	Standard Bus Connection Provisions	Rear-Connect Horizontal/ Vertical Adapter Kit with and without Cover (Kits shipped unassembled)	Fixed Front Connect Breaker Cable-Connected Cable Terminals	Hybrid Connect Breaker: Rear Connect Top—Cable Connect Bottom	Hybrid Connect Breaker: Cable Connect Top—Rear Connect Bottom
Drawout Breaker	Stored energy	Finger clusters	—	—	—	—
Cassette 	—	Rear-connected pre-drilled bus pads		—	—	—
Fixed 	Stored energy	Rear-connected pre-drilled bus pads			—	—

Mounting and Load Connection Configurations—RF Frame

Breaker Type	Breaker Mechanism	Standard Bus Connection Provisions	Rear-Connect Horizontal/ Vertical Adapter Kit with and without Cover (Kits shipped unassembled)
Drawout Breaker 	Stored energy	Finger clusters	—
Cassette	—	Rear-connected pre-drilled bus pads	
Fixed 	Stored energy	Rear-connected pre-drilled bus pads	—

Circuit Breaker Dimensions in Inches (mm) and Weights in lb (kg)

Description	Height		Width		Depth		Weight	
Frame	NF	RF	NF	RF	NF	RF	NF	RF
Fixed—Rear Connect								
Three-pole	13.31 (338.1)	15.65 (397.6)	8.25 (209.6)	13.22 (335.8)	7.15 (181.8)	11.51 (292.4)	45 (20)	120 (55)
Four-pole	13.31 (338.1)	15.65 (397.6)	11.00 (279.4)	19.41 (492.9)	7.15 (181.6)	11.51 (292.4)	62 (28)	155 (71)
Fixed—Front Connect								
Three-pole	15.99 (406.3)	—	8.25 (209.6)	—	7.16 (181.8)	—	45 (20)	120 (55)
Four-pole	15.99 (406.3)	—	11.00 (279.4)	—	7.15 (181.6)	—	62 (28)	155 (71)
Drawout								
Three-pole	14.17 (359.9)	17.96 (456.1)	10.00 (254.0)	15.67 (397.9)	10.50 (266.7)	14.48 (367.8)	87 (40)	211 (96)
Four-pole	14.17 (359.9)	17.96 (456.1)	12.75 (323.9)	18.06 (458.7)	10.50 (266.7)	14.48 (367.8)	109 (50)	258 (117)

Available Front Connect Cable Terminals

	List Number	Connector	Ratings (kA)	To Breaker?	Catalog Number (Three-Pole)
	1	Bus conductor extension (42 kA and below)	42	—	**NRXBUSEXT**
		Bus conductor extension (50 kA and below)	50	—	**NRXBUSEXT**
		Bus conductor extension (65 kA and below)	65	—	**NRXBUSEXT653**
	2	Cable terminals (two holes)	65	Yes	**TA700NB1M**
		With control wire provisions	65	Yes	**TA700NB1MCWT**
	3	Cable terminals (three holes)	65	Yes	**TA1000NB1M**
		With control wire provisions	65	Yes	**TA1000NB1MCWT**
	4	Cable terminals (four holes)	65	Load side only ①	**TA1200NB1M**
		With control wire provisions	65	Load side only ①	**TA1200NB1MCWT**
	5	Cable terminals (three holes for 750 kcmil)	65	Load side only ①	**TA1201NB1M**

Available Rear Connectors for Fixed Breakers or Cassettes (NF-Frame)

	List Number	Connector	Number of Poles	Catalog Number
	1	Universal bus adapter—short	3	**SADP316**
			4	**SADP416**
	2	Universal bus adapter—long	3	**LADP316**
			4	**LADP416**
	3	Rear connect adapter extensions—short (horizontal holes)	3	**SBADPI316**
			4	**SBADPI416**
	4	Rear connect adapter extensions—long (horizontal holes)	3	**LBADPU316**
			4	**LBADPU416**
	5	Front connect	3	**CASADP316**
			4	**CASADP416**

Available Rear Connectors for Fixed Breakers or Cassettes (RF-Frame)

	List Number	Connector	Number of Poles	Catalog Number
	1	Horizontal/vertical kit	3	**RFADP3PU32**
			4	**RFADP4PU32**
	2	Vertical kit	3	**RFADP3PV40**
			4	**RFADP4PV40**
	3	Horizontal/vertical 4000A kit	3	**RFADP3PH40**
			4	**RFADP4PH40**

Note

① For use on line side, user must use catalog number **NRXBUSEXT503** for 50 kA, or **NRXBUSEXT653** for 65 kA.

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire (Number of Conductors)	AWG Wire Catalog Number ①	Metric Wire Range mm^2	Metric Catalog Number ①
Standard Cu/Al Pressure Terminals						
700	Aluminum	Cu/Al	1–500 (2)	**TA700NB1**	50–240	**TA700NB1M**
1000	Aluminum	Cu/Al	3/0–400 (3)	**TA1000NB1**	95–185	**TA1000NB1M**
1200	Aluminum	Cu/Al	4/0–500 (4)	**TA1200NB1**	120–240	**TA1200NB1M**
1200	Aluminum	Cu/Al	500–750 (3)	**TA1201NB1**	300–400	**TA1201NB1M**

Accessory Ratings

Undervoltage Release Ratings

Control Voltages	Frequency	Operational Voltage Range 85%–110%	Dropout Voltage Range 35%–60%	Inrush/Continuous Power Consumption (VA)	Opening Time (ms) -NF	Opening Time (ms) -RF
24	DC	20–26	8–14	425/2	25	37
48	DC	41–53	17–29	750/3	25	37
60	DC	51–66	21–36	825/4	25	37
110–127	50–60 Hz	94–140	44–66	1150/8	25	37
110–125	DC	94–138	44–66	1150/8	25	37
208–240	50–60 Hz	177–264	84–125	1200/8	25	37
220–250	DC	187–275	88–132	1200/8	25	37

Shunt Trip Ratings

Control Voltages	Frequency	Operational Voltage Range 70%–110%	Inrush/ Continuous Power Consumption (VA)	Opening Time (ms) -NF	Opening Time (ms) -RF
24	DC	17–26	400/2	15	22
48	DC	34–53	500/3	15	22
60	DC	42–66	500/4	15	22
110–127	50–60 Hz	77–140	800/8	15	22
110–125	DC	77–138	800/8	15	22
208–240	50–60 Hz	146–264	850/8	15	22

Spring Release Ratings

Control Voltages	Frequency	Operational Voltage Range 85%–110%	Inrush Power Consumption (VA)	Closing Time (ms) -NF	Closing Time (ms) -RF
24	DC	20–26	400	20	35
48	DC	41–53	500	20	35
60	DC	51–66	500	20	35
110–127	50–60 Hz	94–140	750	20	35
110–125	DC	94–138	750	20	35
208–240	50–60 Hz	177–264	800	20	35

Note

① Single terminals individually packed.

Motor Operator

Control Voltages	Frequency	Operational Voltage Range 85%–110%	Running Current (A)	Typical Inrush Current	Power Consumption (VA)	Maximum Charging Time (sec)
NF						
24	DC	20–26	6	325%	160	4
48	DC	41–53	3	500%	150	3
60	DC	51–66	2	350%	150	4
110–127	50–60 Hz	94–140	2	300%	280	3
110–125	DC	94–138	1	500%	150	3
208–240	50–60 Hz	177–264	1	1000%	280	4
220–250	DC	187–275	1	1000%	280	4
RF						
24	DC	20–26	7	350%	200	6
48	DC	41–53	3	450%	175	6
60	DC	51–66	2	450%	225	6
110–127	50–60 Hz	94–140	3	300%	425	6
110–125	DC	94–138	2	375%	275	6
208–240	50–60 Hz	177–264	1.5	300%	400	6
220–250	DC	187–275	1	400%	250	6

Control Voltages and Currents

Control Voltages	24 Vdc	48 Vdc	60 Vdc	110–125 Vdc	110–127 Vac	220–250 Vdc	208–240 Vac
Current							
Close current (inrush)	14	10	8	7	7	4	4
Shunt trip current (ST)—(inrush/continuous)	16/0.08	10/0.06	8/0.07	7/0.07	7/0.07	4/0.04	4/0.04
NF—Charge motor current (inrush/continuous)	20/6	15/3	7/2	5/1	6/2	10/1	10/1
RF—Charge motor current (inrush/continuous)	23/7	14/3	14/3	8/2	9/3	4/1	5/1.5
Operating Voltage Rating							
Close	20–26	41–53	51–66	94–138	94–140	187–275	177–264
Open	17–26	34–53	42–66	77–138	77–140	154–275	146–264
Charge—NF	20–26	41–53	51–66	94–138	94–140	187–275	177–264
Charge—RF	26–26	41–53	51–66	94–138	94–140	187–275	177–264

Overcurrent Trip Switch

Control Voltages	Frequency	Contact Rating (Amperes)
250	50–60 Hz	10
125	DC	0.5
250	DC	0.25

Auxiliary Switch

Control Voltages	Frequency	Contact Rating (Amperes)
250	50–60 Hz	10
125	DC	0.5
250	DC	0.25

Breaker Position/Continuity—NF Frame

Breaker Position	Continuity Between Red and Black Lead Pairs		Continuity Between Blue and Black Lead Pairs	
Open	No		47 and 45;	48 and 49
	No		53 and 51;	54 and 55
Closed	46 and 45;	50 and 49	No	
	52 and 51;	56 and 55	No	

Breaker Position/Continuity—RF Frame

Breaker Position	Continuity Between Red and Black Lead Pairs		Continuity Between Blue and Black Lead Pairs	
Open	No		59 and 57;	60 and 61
	No		65 and 63;	66 and 67
	No		71 and 69;	72 and 73
	No		77 and 75;	78 and 79
	No		83 and 81;	84 and 85
	No		89 and 87;	90 and 91
Closed	58 and 57;	62 and 61	No	
	64 and 63;	68 and 67	No	
	70 and 69;	74 and 73	No	
	76 and 75;	80 and 79	No	
	82 and 81;	86 and 85	No	
	88 and 87;	92 and 91	No	

Series NRX with Digitrip

Series NRX NF Drawout Breaker

Series NRX Fixed Front Connect Breaker with Bus Extensions (Optional)

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	
Catalog Number Selection	**V4-T3-49**
Technical Data and Specifications	**V4-T3-51**
Medium Voltage Circuit Breakers	**V4-T3-55**

Series NRX Low Voltage Power Circuit Breakers with Digitrip

Product Description

Series NRX is a low voltage power circuit breaker suitable for UL 1558, UL 891, and IEC switchgear and switchboards. The compact size and weight of three-pole drawout with cassette Series NRX, see **Page V4-T3-51**, allows for a 24.00 (609.6 mm) switchgear enclosure.

The breaker ratings are:

- 800 A for UL 1066
- 800 A, 1200 A for UL 489
- 630–1600 A IEC 60947-2 from a voltage range of 220–725 Vac

Application Description

The Series NRX is a compact globally certified low voltage power (air) circuit breaker. It is rated for 800 A (UL 1066), 800 A and 1200 A (UL 489) and 630–1600 A (IEC 60947-2) with an interrupting capacity of 65 kA with short time withstand at 42 kA at the 440/480 Vac level.

The Series NRX circuit breaker provides all the capabilities of a power circuit breaker in the compact size of a molded case breaker. It offers you the same protection and performance—along with increased flexibility—at half the size of a typical power circuit breaker.

The dimensions and design of Series NRX allows up to eight UL 1066 or UL 489 breakers in a 24-inch (600 mm) wide structure. The one frame size, regardless of ampere rating, reduces drawing conversion, structure integration time and parts inventory for several board, gear and machinery applications.

Features, Benefits and Functions

Series NRX utilizes several innovative technologies:

- Rogowski coil—does not saturate like iron core sensors, and one sensor accommodates 200–1600 ampere range. You never have to change a sensor and CTs are not required
- Tension clamp secondary terminals—10 A continuous rating at 600 V meets UL/CSA/RoHS and UL-94 V0. Mounted directly to fixed breaker or drawout cassette, they reduce wiring throughout enclosure and provide clean, organized wiring schemes
- Breaker-mounted communication modules—communication modules for INCOM™, Modbus® and PROFIBUS mount directly to the cassette, reducing the space and room required in gear for communication capability
- "Direct Drive" mechanism—symmetrically loaded forces of the two-staged stored energy mechanism improves robustness, reliability, and achieves improved breaker life ratings
- Fold-up cassette—with this simple design, all items in a cassette are replaceable without removing the cassette from the cell
- "Arc chute" design
- Breaker-mounted racking or levering-in device—Racking device is mounted on the breaker, decreasing the width of the cassette, because the cassette is not burdened with the cost or parts of the lev-in
- Plug-N-Play accessories—No special tools needed. Accessory comes with plug and wires ready to install
- Arcflash Reduction Maintenance System—Eaton's patented technology provides maintenance staff with improved safety of downstream maintenance locations using a simple and reliable method to reduce fault clearing times and energy during an arc flash event (radiation, sound, pressure, temperature). Arcflash Reduction Maintenance System uses a separate analog trip circuit, providing faster signal processing and interruption times than the standard (digital) "instantaneous" protection. The Arcflash Reduction Maintenance System function is activated either directly on the circuit breaker through a local switch or remotely through communications or a digital input

The use of these technologies allows Series NRX to offer a life of 20,000 mechanical operations and 10,000 electrical operations with a high degree of reliability.

Standards and Certifications

- UL 1066 (low voltage AC power circuit breakers used in enclosures)
- UL 489 (molded case circuit breakers, molded case switches and circuit breaker enclosures)
- EN 45011
- CEI EN 60947
- BS EN 60439-1 Form 4b
- IEC 60439-1 (low voltage switchgear and controlgear assemblies)
- IEC 60947-1 (low voltage switchgear and controlgear —Part 1 general rules)
- IEC 60947-2 (low voltage switchgear and controlgear —Part 2 circuit breakers)
- IEC 60947-3 (switches, disconnectors, switch-disconnectors and fuse-combination units)
- CSA 22.2 (molded case circuit breakers, molded case switches and circuit breaker enclosures)
- ANSI C37.51 (metal-enclosed low voltage AC power circuit breaker switchgear assemblies—conformance test procedures)
- ANSI C37.20.1 (metal-enclosed low voltage power circuit breaker switchgear)
- ANSI C37.60 (requirements for overhead, pad-mounted dry-type and submersible automatic reclosers and fault interrupters for AC systems)
- ANSI C37.50 (low voltage AC power circuit breakers used in enclosures—test procedures)
- ANSI C37.17 (for trip devices for AC and general purpose DC low voltage power circuit breakers)
- ANSI C37.16 (low voltage power circuit breakers and AC power circuit protectors—preferred ratings, related requirements, and application recommendations)
- ANSI C37.13 (IEEE® standard for low voltage AC power circuit breakers used in enclosures)
- CCC—China
- KEMA (&CB)
- UL 891 (deadfront switchboard)
- UL 1558 (metal-enclosed low voltage power circuit breaker switchgear)

Reference Information

List of Instruction Leaflets and Manuals

Description	Publication Number
Instruction Book for Fixed and Drawout Breaker/Cassette	MN01301001E
IL Drawout Circuit Breaker and Cassette Rejection Interlocks	IL01301006E
IL Auxiliary Switch in Right Accessory Tray	IL01301007E
IL UVR/ST/OTS in Left Accessory Tray	IL01301008E
IL Motor Operator	IL01301010E
IL Spring Release Device and Latch Check Switch (Numbers 5 and 6 are Combining into one Document)	IL01301010E
IL Door Escutcheon and Gasket Kit	IL01301012E
IL Drawout Cassette IP 20 Shutters	IL01301013E
IL Fixed Breaker Arc Hood Kit	IL01301014E
IL Fixed Breaker Front/Rear/Cable Connectors	IL01301015E
IL Drawout Cassette Front/Rear/Cable Connectors	IL01301016E
IL Racking Device Levering Device	IL01301018E
IL Mechanical Pop-Out Indicator and Interlocked Indicator	IL01301019E
IL Breaker and Cassette Phase Barriers	IL01301021E
IL Cassette Rails	IL01301025E
IL Mounting Feet	IL01301030E
IL Surface Mount	IL01301036E
IL Terminal Blocks	IL01301037E
IL Modbus Communication Adapter Module	IL01301034E
IL INCOM Communication Adapter Module	IL01301033E
IL Digitrip 520 and 520M Manual	IL70C1619H01
IL IP55 Cover	IL01301038E
PROFIBUS Communication Module	IL01301035E
IL Kirk Key Lock	IL01301039E
IL Ronis Key Lock	IL01301040E
IL Pushbutton Covers	IL01301041E

Catalog Number Selection

Series NRX Type NF-Frame Circuit Breaker (Exclusionary Rules Apply)

N S S6 08 3 W 52 8 A B A N 4 X N D X

Breaker Frame Size
N = Type NF, 630–1600 A, (70 mm pole spacing)

Standard, Mechanism, Device
S = UL 1066, stored energy, power breaker
X = UL 489, stored energy, insulated case breaker
E = IEC 60947-2, stored energy, air breaker

Fault Current Rating
S4 = 42 kA at 480 Vac UL or 415 Vac IEC
S5 = 50 kA at 480 Vac UL or 415 Vac IEC
S6 = 65 kA at 480 Vac UL or 415 Vac IEC

Frame Rating (Amperes)
07 = 630 (IEC only)
08 = 800
10 = 1000 (IEC only)
12 = 1200 (UL only)
13 = 1250 (IEC only)
16 = 1600 (On NF: IEC only)

Poles, Phasing
3 = Three-pole, ABC
4 = Four-pole, NABC

Mounting Configuration
W = Drawout
B = Fixed mount rear connected with side mounting brackets
R = Fixed mount rear connected without side mounting brackets
F = Front connected, fixed mount, for bus or cable connections with side mounting brackets

Rating Plug (Amperes)
1 = 200
2 = 250
3 = 300
4 = 400
5 = 500
6 = 600
7 = 630
8 = 800
A = 1000
B = 1200
C = 1250
D = 1600

Shunt Trip
N = No shunt trip
A = 110–127 Vac/Vdc
R = 208–240 Vac/Vdc
L = 24 Vdc
H = 48 Vdc
S = 60 Vdc

Motor Operator
M = Manually operated
B = 110–125 Vac
W = 110–125 Vdc
T = 208–250 Vac
P = 220–250 Vdc
L = 24 Vdc
H = 48 Vdc
S = 60 Vdc

Spring Release, Latch Check Switch
N = No spring release, no LCS
E = No spring release, LCS wired external
A = 110–127 Vac/Vdc, no LCS
B = 110–127 Vac/Vdc, spring release LCS
C = 110–127 Vac/Vdc, LCS wired external
R = 208–240 Vac/Vdc, no LCS
S = 208–240 Vac/Vdc, spring release LCS
T = 208–240 Vac/Vdc, LCS wired external
L = 24 Vdc, no LCS
P = 24 Vdc, spring release LCS
Q = 24 Vdc, LCS wired external
H = 48 Vdc, no LCS
J = 48 Vdc, spring release LCS
K = 48 Vdc, LCS wired external
1 = 60 Vdc, no LCS
2 = 60 Vdc, spring release LCS
3 = 60 Vdc, LCS wired external

Trip Unit, Power Supply

SW = Switch—no MCR—42 kA for IEC and UL 1066 (non-auto)
22 = 520 LI, no ZSI
52 = 520 LSI, no ZSI
53 = 520 LSI, with ZSI
5G = 520 LSIG, no ZSI
5H = 520 LSIG, with ZSI
M2 = 520M LSI, no ZSI, 24 Vdc
M3 = 520M LSI, with ZSI, 24 Vdc
MA = 520M LSIA, no ZSI, 24 Vdc
MB = 520M LSIA, with ZSI, 24 Vdc
MG = 520M LSIG, no ZSI, 24 Vdc
MH = 520M LSIG, with ZSI, 24 Vdc
R2 = 520M LSI, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
R3 = 520M LSI, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
RA = 520M LSIA, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
RB = 520M LSIA, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
RG = 520M LSIG, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
RH = 520M LSIG, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1A = 1150 LSI, with ZSI, 24 Vdc
1B = 150 LSI, with ZSI , 24 Vdc
12 = 1150i LSI, no ZSI, 24 Vdc
13 = 1150i LSI, with ZSI, 24 Vdc
1E = 1150 LSIA, no ZSI, 24 Vdc
1F = 1150 LSIA, with ZSI, 24 Vdc
1L = 1150 LSIG, no ZSI, 24 Vdc
1M = 1150 LSIG, with ZSI, 24 Vdc
14 = 1150 LSIGA, no ZSI, 24 Vdc
15 = 1150 LSIGA, with ZSI, 24 Vdc
1C = 1150 LSI, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1D = 1150 LSI, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
16 = 1150i LSI, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
17 = 1150i LSI, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1J = 1150 LSIA, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1K = 1150 LSIA, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1R = 1150 LSIG, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
1S = 1150 LSIG, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
18 = 1150i LSIGA, no ZSI, 24 Vdc, with Arcflash Reduction Maintenance System
19 = 1150i LSIGA, with ZSI, 24 Vdc, with Arcflash Reduction Maintenance System

Series NRX Type NF-Frame Circuit Breaker (Exclusionary Rules Apply), continued

N S S6 08 3 W 52 8 A B A N 4 X N D X

UVR, Second Shunt Trip
- **N** = None
- **A** = 110–125 Vac/Vdc UVR
- **R** = 220–250 Vac/Vdc UVR
- **L** = 24 Vdc UVR
- **H** = 48 Vdc UVR
- **S** = 60 Vdc UVR
- **G** = 32 Vdc UVR
- **1** = 110–127 Vac/Vdc second shunt trip
- **2** = 208–240 Vac/Vdc second shunt trip
- **4** = 24 Vdc second shunt trip
- **8** = 48 Vdc second shunt trip
- **9** = 60 Vdc second shunt trip

Auxiliary, Switches, Label Language
- **E** = No auxiliary switches, no label (parent)
- **2** = 2 Form C, English
- **4** = 4 Form C, English

	Trip Indicator and Bell Alarm	OTS	Secondary Terminal Blocks
N	None	None	Per breaker options
X	Trip indicator	None	Per breaker options
Z	Trip indicator	2 Form C	Per breaker options
M	Interlock trip indicator	None	Per breaker options
Y	Interlock trip indicator	2 Form C	Per breaker options
1	None	None	Full complement
2	Trip indicator	None	Full complement
3	Trip indicator	2 Form C	Full complement
4	Interlock trip indicator	None	Full complement
5	Interlock trip indicator	2 Form C	Full complement

	Padlock Provisions	Key Lock Provisions	Operations Counter
N	No	None	No
A	No	—	Provided
B	Yes (plastic/plastic)	—	No
C	Yes (plastic/plastic)	—	Provided

Drawout Breaker Shipping, Fixed Breaker Terminals (Door Frame Kit ships as standard unless noted otherwise)
- **D** = Drawout breaker shipping alone, without door frame kit
- **C** = Drawout breaker shipping in cassette, no shutters, no terminals
- **1** = Drawout breaker shipping in cassette, no shutters, short vertical/horizontal
- **2** = Drawout breaker shipping in cassette, no shutters, long vertical/horizontal
- **4** = Drawout breaker shipping in cassette, with shutters, short vertical/horizontal
- **5** = Drawout breaker shipping in cassette, with shutters, long vertical/horizontal
- **9** = Drawout breaker shipping in cassette, no shutters, no terminals
- **F** = Fixed terminal adapters for rear connect, with mounting feet, short vertical/horizontal adapter kit
- **H** = Rear connect, fixed breaker, with long vertical/horizontal adapters
- **J** = Front connect fixed breaker, with no terminal adapters
- **K** = Rear connect, fixed breaker, no terminal adapters

Future Use
- **X** = All product

Series NRX Type NF-Frame Cassette

NX 12 3 F A B Z S N N N C

Cassette Family and Breaker Frame
- **NS** = UL 1066 N-Frame
- **NX** = UL 489 N-Frame
- **NE** = IEC N-Frame

Continuous Ampere Range
- **08** = 800 (UL 1066)
- **12** = 800–1200 (UL 489)
- **16** = 630–1600 (IEC)

Poles and Phasing (Facing Front of Breaker)
- **3** = Three-pole ABC
- **4** = Four-pole NABC

Load Terminal Connections
- **F** = With flat tapped pads only
- **G** = With vertical/horizontal bus adapter kit (short style)
- **H** = With front-connected kit
- **N** = No cassette stabs (interunit only)

Arc Hood
- **A** = Arc hood installed (default)

Door Frame Gasket and Rejection Kits
- **B** = Door kit included (default), with rejection kit
- **D** = Door kit included, no rejection kit
- **R** = Not included, with rejection kit
- **N** = Not included, with rejection kit

Cell Switch Options (available on Breaker + Cassette or Cassette Only)
- **W** = None
- **Z** = Cell switch installed

Future
- **N** = None

Future
- **N** = None

Secondary Contact Terminals Installed
- **N** = None
- **B** = Breaker defined, when breaker ships in cassette
- **F** = Full complement
- **C** = Common options when cassette ships alone

Shutters
- **N** = Not included (default)
- **S** = Included

Cassette Shipping
- **C** = Cassette only
- **B** = Breaker shipped in cassette

Technical Data and Specifications

UL 1066 Ratings

Description	Rating
Continuous current rating (amperes)	800
Short-Circuit Rating (kA)	
254 Vac	85
508 Vac	65
635 Vac	35
Short-time withstand (kA) ①	42

UL 489 Ratings

Description	Rating	Rating
Continuous current rating (amperes)	800	1200
Short-Circuit Rating (kA)		
240 Vac	85	85
480 Vac	65	65
600 Vac	42	42
Short-time withstand (kA)	42	42

IEC 60947-2 Ratings

Description	Rating		Rating		Rating	
Continuous current rating (amperes)	630 and 800		1000 and 1250		1600	
Short-circuit rating (kA)	Icu	Ics	Icu	Ics	Icu	Ics
240/254 Vac	85	50	85	50	85	50
415/435 Vac	65	50	65	50	65	50
690/725 Vac	42	42	42	42	42	42
Short-time withstand = Icw (kA)	42	42	42	42	42	42

Approximate Dimensions in Inches (mm)

Series NRX Three-Pole Drawout with Cassette

Height	Width	Depth	Lb (kg)
14.18 (360.2)	10.02 (254.5)	10.68 (271.3)	85.00 (38.59)

Series NRX Three-Pole Front Connect Fixed Breaker

Height	Width	Depth	Lb (kg)
16.00 (406.4)	8.25 (209.6)	7.15 (181.6)	—

Rear Fixed Circuit Breaker and Drawout with Cassette

Breaker Type	Height	Width	Depth	Lb (kg)
Fixed				
Three-pole	13.18 (334.8)	8.25 (209.6)	7.15 (181.6)	33.58 (15.23)
Four-pole	13.18 (334.8)	11.00 (279.4)	7.15 (181.6)	44.40 (20.14)
Drawout with Cassette				
Three-pole	14.18 (360.2)	10.02 (254.5)	10.69 (271.5)	85.20 (38.65)
Four-pole	14.18 (360.2)	12.69 (322.3)	10.69 (271.5)	104.00 (47.17)

Mounting and Load Connection Configurations

Breaker Type	Breaker Mechanism	Standard Bus Connection Provisions	Rear-Connect Horizontal/Vertical Adapter Kit With and Without Cover (Kits Shipped Unassembled)	Rear Connect Breaker Front-Connect Horizontal/Vertical Adapter Kit With and Without Cover (Kits Shipped Separately)	Fixed Front Connect Breaker Cable-Connected Cable Terminals
Drawout Breaker	Stored energy	Finger clusters	—	—	—
Cassette	—	Rear-connected pre-drilled bus pads		—	—
Fixed	Stored energy	Rear-connected pre-drilled bus pads			

Note

① 35 kAIC short-time withstand at 635 V level only. All other voltages 42 kAIC short-time withstand.

Available Front Connect Cable Terminals

	List Number	Connector	Ratings (kA)	To Breaker?	Catalog Number (Three-Pole)
	1	Bus conductor extension (42 kA and below)	42	--	**NRXBUSEXT**
		Bus conductor extension (50 kA and below)	50	--	**NRXBUSEXT**
		Bus conductor extension (65 kA and below)	65	--	**NRXBUSEXT653**
	2	Cable terminals (two holes)	65	Yes	**TA700NB1M**
		With control wire provisions	65	Yes	**TA700NB1MCWT**
	3	Cable terminals (three holes)	65	Yes	**TA1000NB1M**
		With control wire provisions	65	Yes	**TA1000NB1MCWT**
	4	Cable terminals (four holes)	65	Load side only ①	**TA1200NB1M**
		With control wire provisions	65	Load side only ①	**TA1200NB1MCWT**
	5	Cable terminals (three holes for 750 kcmil)	65	Load side only ①	**TA1201NB1M**

Available Rear Connectors for Fixed Breakers or Cassettes

	List Number	Connector	Catalog Number
	1	Universal bus adapter—short	**SADP316** **SADP416**
	2	Universal bus adapter—long	**LADP316** **LADP416**
	3	Rear connect adapter extensions—short (horizontal holes)	**SBADPI316** **SBADPI416**
	4	Rear connect adapter extensions—long (horizontal holes)	**LBADPU316** **LBADPU416**

Line and Load Terminals

Maximum Breaker Amperes	Terminal Body Material	Wire Type	AWG Wire (Number of Conductors)	AWG Wire Catalog Number ②	Metric Wire Range mm^2	Metric Catalog Number ②
Standard Cu/Al Pressure Terminals						
700	Aluminum	Cu/Al	1–500 (2)	**TA700NB1**	50–240	**TA700NB1M**
1000	Aluminum	Cu/Al	3/0–400 (3)	**TA1000NB1**	95–185	**TA1000NB1M**
1200	Aluminum	Cu/Al	4/0–500 (4)	**TA1200NB1**	120–240	**TA1200NB1M**
1200	Aluminum	Cu/Al	500–750 (3)	**TA1201NB1**	300–400	**TA1201NB1M**

Notes

① For use on line side, user must use catalog number **NRXBUSEXT503** for 50 kA, or **NRXBUSEXT653** for 65 kA.

② Single terminals individually packed.

Accessory Ratings

Shunt Trip

Control Voltages	Frequency	Operational Voltage Range 70–110%	Inrush/Continuous Power Consumption (VA)	Opening Time (ms)
24	DC	17–26	500/5	25
48	DC	34–53	530/5	25
110–127	50–60 Hz	77–140	540/5	25
110–125	DC	77–138	540/5	25
208–240	50–60 Hz	146–264	500/5	25
220–250	DC	154–275	515/5	25

UVR

Control Voltages	Frequency	Operational Voltage Range 85–110%	Dropout Volts 35–60%	Inrush/Continuous Power Consumption (VA)	Opening Time (ms)
24	DC	20–26	8–14	500/5	50
32	DC	27–35	11–19	620/5	50
48	DC	41–53	17–29	850/5	50
110–127	50–60 Hz	94–140	44–94	890/5	50
110–125	DC	94–138	44–94	890/5	50
208–240	50–60 Hz	177–264	84–125	910/5	50
220–250	DC	187–275	88–132	910/5	50
380–415	AC	323–457	145–228	960/5	50
480	AC	408–528	168–288	800/8	50
600	AC	510–660	210–360	800/12	50

Spring Release

Control Voltages	Frequency	Operational Voltage Range 70–110%	Inrush Power Consumption (VA)	Closing Time (ms)
24	DC	17–26	500	25
48	DC	34–53	530	25
110–127	50–60 Hz	77–140	540	25
110–125	DC	77–138	540	25
208–240	50–60 Hz	146–264	500	25
220–250	DC	154–275	515	25

OCT/OTS

Control Voltages	Frequency	Contact Rating (Amperes)
250	50–60 Hz	10
125	DC	0.5
250	DC	0.25

Auxiliary Switch

Control Voltages	Frequency	Contact Rating (Amperes)
250	50–60 Hz	10
125	DC	0.5
250	DC	0.25

Breaker Position/Continuity

Breaker Position	Continuity Between Red and Black Lead Pairs	Continuity Between Blue and Black Lead Pairs
Open	NO	45 and 43
	NO	46 and 47
	NO	51 and 49
	NO	52 and 53
Closed	44 and 43	NO
	48 and 47	NO
	50 and 49	NO
	54 and 53	NO

Motor Operator

Control Voltages	Frequency	Operational Voltage Range 85–110%	Running Current (A)	Typical Inrush Current	Power Consumption (VA)	Maximum Charging Time (Sec)
24	DC	20–26	5	500%	150	3
48	DC	41–53	3	500%	150	3
110–127	50–60 Hz	94–140	2	300%	280	3
110–125	DC	94–138	1	500%	150	3
208–240	50–60 Hz	177–264	1	1000%	280	4
220–250	DC	187–275	1	1000%	280	4

Control Voltages and Currents

Control Voltages	24 Vdc	48 Vdc	110–125 Vdc	110–127 Vac	220–250 Vdc	208–240 Vac
Current						
Close current (inrush)	21	11	5	5	2	2
Shunt trip current (ST)—(inrush/continuous)	21 / .2	11 / .1	5 / .04	5 / .04	2 / .02	2 / .02
Charge motor current—(inrush/continuous)	TBD	TBD	5 / 1	6 / 2	10 / 1	10 / 1
Operating Voltage Rating						
Close	17–26	34–53	77–138	77–140	154–275	146–264
Trip	17–26	34–53	77–138	77–140	154–275	146–264
Charge	20–26	41–53	94–138	94–140	187–275	177–264

Type VCP-W/VCP-T Medium Voltage Vacuum Circuit Breaker

Contents

Description	*Page*
Low Voltage Power Circuit Breakers	**V4-T3-2**
Magnum DS Low Voltage Power Circuit Breakers	**V4-T3-6**
Magnum MDSL Current Limiting Power Circuit Breaker	**V4-T3-12**
Magnum SB Low Voltage Insulated Case Circuit Breakers	**V4-T3-15**
Magnum IEC Rated Air Circuit Breakers	**V4-T3-23**
Magnum DC (Direct Current) Low Voltage Switches	**V4-T3-33**
Series NRX Low Voltage Power Circuit Breakers with PXR	**V4-T3-35**
Series NRX Low Voltage Power Circuit Breakers with Digitrip	**V4-T3-47**
Medium Voltage Circuit Breakers	
Features, Benefits and Functions	**V4-T3-56**
Product Selection	**V4-T3-57**

Medium Voltage Circuit Breakers

Product Description

Breakers and structures for switchgear assemblies:

ANSI

- VCP-W medium voltage circuit breakers
  - 5/15 kV VCP-W (K>1, K=1, narrow design, extra-capability and generator circuit breakers available)
  - 27 kV and 38 kV (extra-capability circuit breakers available)
  - Ground and test devices
  - Dummy elements
- VCP-T medium voltage circuit breakers
  - 5/15 kV VCP-T (capacitor switching and magnetic actuated circuit breakers available)
  - Ground and test devices
  - Dummy elements

IEC

- T-VAC medium voltage circuit breakers
  - 5/15 kV VCP-T (capacitor switching circuit breakers available)
  - Ground and test devices
  - Dummy elements
- VCP-W IEC medium voltage circuit breakers
  - 3.6/7.2/12/17.5 kV
  - 24 kV

OEM Structures

- Metal-clad, compartmented design
- Barebones
- Power modules
- Mini modules
- Breaker compartment kits

Application Description

Eaton's medium voltage circuit breakers offer the latest in vacuum technology, providing superior control and protection of medium voltage power equipment in utility, industrial, commercial, mining and marine installations. Built in a state-of-the-art ISO® 9002 certified facility, they meet and exceed all ANSI and IEC requirements. Available in drawout configurations, Eaton's vacuum circuit breakers are a result of our ongoing commitment to research and development, which have resulted in significant breakthrough technologies. Each breaker is provided with its unique Quality Assurance Certificate that documents all tests and inspections performed.

Features, Benefits and Functions

VCP-W Standard Features

- Eaton's maintenance-free vacuum interrupters with visual contact erosion indicator
- Non-sliding/non-rolling V-Flex™ current transfer system
- Glass polyester insulation
- Cycloaliphatic epoxy insulation (optional with Type VCPW-SE breakers) for 27 kV and 38 kV breakers
- Front-accessible operating mechanism
- Electrically operated trip-free, spring stored energy mechanism
- Interlocks that prevent moving a closed circuit breaker into or out of the connected position
- Closing springs automatically discharge before moving the circuit breaker into or out of the enclosure
- Provisions for manual charging of closing springs
- Manual close and trip pushbuttons
- Operations counter
- Closing spring charged/ discharged indicator
- Circuit breaker Open/ Closed indicator
- Auxiliary switch with 2A/3B for DC and 1A/3B for AC spare contacts
- Spring charging motor, close coil, trip coil, latch check switch and anti-pump relay

VCP-T Standard Features

- Small without compromise—significantly smaller and lighter than comparable breakers
- Grounded steel barrier between mechanism and primary conductors
- Spring loaded, silver-plated primary disconnects (drawout breaker)
- Silver-plated primary connections (fixed circuit breaker)
- Manual charging of closing springs (includes shunt trip)
- Integral spring charging handle
- Auxiliary switch (5a and 5b contacts)
- Mechanical operations counter
- 24, 48, 125 and 250 Vdc, 120 and 240 Vac control
- Shunt trip
- ON and OFF pushbuttons
- Integral lifting hooks
- Through- or behind-door operation
- Identified/dedicated secondaries
- Secondary umbilical cord (drawout circuit breaker)
- Secondary disconnect block (fixed circuit breaker)
- Two-step stored energy mechanism
- O–0.3s–CO–15s–CO
- Anti-pump
- Trip free
- Latch check switch
- Visible contact erosion indicator
- Visible contact wipe indicator
- Disconnect, Test and Connect (drawout circuit breaker)
- Integral levering mechanism (drawout circuit breaker)
- Field-installable accessories

Standards and Certifications

- Designed, tested and certified in accordance with ANSI and IEC standards
- Applicable ANSI standards C37.04-1979 or 1999, C37.09-1979 or 1999, C37.06-2000 and C37.013
- Internal arc resistance tested to IEC 298, Appendix AA, 25 kA for 1 second
- Drawout circuit breaker fully qualified to IEC 56 by testing inside the IEC 298 switchgear cubicle
- IEEE C37.013 and amendment C37.013a-2007

Product Selection

Please contact your Eaton sales representative for additional product information and to review your specific application and required product configuration.

Technical Data and Specifications

ANSI Standards

ANSI Standard Ratings—VCP-W Vacuum Circuit Breaker Types Rated on Symmetrical Current Rating Basis—Standard Circuit Breakers ①

	Circuit Breaker Type								
Description	**50 VCP-WND250**	**50 VCP-W250**	**50 VCP-W350**	**50 VCP-W500 (63 kA)**	**75 VCP-W500**	**150 VCP-W500**	**150 VCP-W750**	**150 VCP-W1000**	**150 VCP-W1500 (63 kA)**
Identification									
Nominal voltage class kV	4.16	4.16	4.16	4.16	7.2	13.8	13.8	13.8	13.8
Nominal three-phase MVA class	250	250	350	—	500	500	750	1000	—
Rated Values									
Voltage Maximum voltage E kV rms	4.76	4.76	4.76	4.76	8.25	15	15	15	15
Voltage range factor K ②	1.24	1.24	1.19	1.00	1.25	1.30	1.30	1.30	1.00
Insulation Level Withstand test voltage									
Power frequency (1 min.) kV rms	19	19	19	19	36	36	36	36	36
Impulse kV peak	60	60	60	60	95	95	95	95	95
Current Continuous current at 60 Hz amperes	1200	1200	1200	1200	1200	1200	1200	1200	1200
		2000	2000	2000	2000	2000	2000	2000	2000
		3000	3000	3000	3000	3000	3000	3000	3000
Short-circuit current (at rated max. kV) I kA rms	29	29	41	63	33	18	28	37	63
Interrupting time cycles	5	5	5	5	5	5	5	5	5
Permissible tripping delay Y seconds	2	2	2	2	2	2	2	2	2
Maximum voltage divided by K E/K kV rms ②	3.85	3.85	4.0	4.76	6.6	11.5	11.5	11.5	15.0
Current Values Maximum symmetrical interrupting capability Short-time current K x 1 kA rms ②	36	36	49	63	41	23	36	48	63
Closing and latching capability kA peak	97	97	132	170	111	62	97	130	170
Closing and latching momentary capability	58	58	78	101	66	37	58	77	101
Weight Lb (kg) 1200 A	345 (157)	350 (159)	460 (209)	525 (238)	375 (170)	350 (159)	350 (159)	460 (209)	525 (238)
2000 A	345 (157)	410 (186)	490 (223)	530 (241)	410 (186)	410 (186)	410 (186)	490 (223)	530 (241)
3000 A	345 (157)	525 (238)	525 (238)	550 (250)	525 (238)	525 (238)	525 (238)	525 (238)	550 (250)

Notes

① Applicable ANSI Standards C37.04-1999, C37.06-2000 (including both K >1 and K =1 ratings), and C37.09-1999.

② See *Consulting Application Guide* for further information.

ANSI Standard Ratings—VCP-W Vacuum Circuit Breaker Types Rated on Symmetrical Current Rating Basis—Extra Capability Breakers ①

Description	Circuit Breaker Type 50 VCP-W25C	50 VCP-W40C	50 VCP-W50C	50 VCP-W63C	75 VCP-W50C	150 VCP-W25C	150 VCP-W40C	150 VCP-W50C	150 VCP-W63C
Identification									
Nominal voltage class kV	4.16	4.16	4.16	4.16	7.2	13.8	13.8	13.8	13.8
Nominal three-phase MVA class	—	—	—	—	—	—	—	—	—
Rated Values									
Voltage Maximum voltage E kV rms	5.95	5.95	5.95	5.95	10.3	17.5	17.5	17.5	15.0
Voltage range factor K ②	1.00	1.00	1.00	1.00	1.00	1.00	1.00	1.00	1.00
Insulation Level Withstand test voltage									
Power frequency (1 min.) kV rms	24	24	24	24	42	42	42	42	42
Impulse kV peak	75	75	75	75	95	95	95	95	95
Current Continuous current at 60 Hz amperes	1200	1200	1200	1200	1200	1200	1200	1200	1200
	2000	2000	2000	2000	2000	2000	2000	2000	2000
	3000	3000	3000	3000	3000	3000	3000	3000	3000
Short-circuit current (at rated max. kV) I kA rms	25	40	50	63	50	25	40	50	63
Interrupting time cycles	3	3	3	3	3	3	3	3	3
Permissible tripping delay Y seconds	2 ③	2 ③	2 ③	2 ③	2 ③	2 ③	2 ③	2 ③	2 ③
Maximum voltage divided by K E/K kV rms ②	5.95	5.95	5.95	5.95	10.3	17.5	17.5	17.5	15.0
Current Values Maximum symmetrical interrupting capability Short-time current K x 1 kA rms ②	25	40	50	63	50	25	40	50	63
Closing and latching capability kA peak	97	139	139	175	139	97	139	139	175
Closing and latching momentary capability	58	83	83	104	83	58	83	83	104
Weight Lb (kg) 1200 A	350 (159)	460 (209)	525 (238)	350 (159)	460 (209)	350 (159)	350 (159)	460 (209)	525 (238)
2000 A	410 (186)	490 (223)	530 (241)	410 (186)	490 (223)	410 (186)	410 (186)	490 (223)	530 (241)
3000 A	525 (238)	525 (238)	550 (250)	525 (238)	525 (238)	525 (238)	525 (238)	525 (238)	550 (250)

Notes

① Applicable ANSI Standards C37.04-1999, C37.06-2000 (including both K >1 and K =1 ratings), and C37.09-1999.

② See *Consulting Application Guide* for further information.

③ Tested for 3 seconds.

ANSI Standard Ratings—VCP-W Vacuum Circuit Breaker Types Rated on Symmetrical Current Rating Basis—Generator Breakers (to ANSI C37.013) ①

Description	Circuit Breaker Type 50 VCP-WG50	50 VCP-WG63	50 VCP-WG75	150 VCP-WG50	150 VCP-WG63	150 VCP-WG75
Identification						
Nominal voltage class kV	4.16	4.16	4.16	13.8	13.8	13.8
Nominal three-phase MVA class	—	—	—	—	—	—
Rated Values						
Voltage						
Maximum voltage E kV rms	4.76	4.76	4.76	15.0	15.0	15.0
Voltage range factor K ②	1.00	1.00	1.00	1.00	1.00	1.00
Insulation Level						
Withstand test voltage						
Power frequency (1 min.) kV rms	19	19	19	36	36	36
Impulse kV peak	60	60	60	95	95	95
Current						
Continuous current at 60 Hz amperes	1200	1200	1200	1200	1200	1200
	2000	2000	2000	2000	2000	2000
	3000	3000	3000	3000	3000	3000
	4000	4000	4000	4000	4000	4000
Short-circuit current (at rated max. kV) kA rms	50	63	75	50	63	75
Interrupting time cycles						
1200 A	3	3	3	3	3	3
2000 A	3	3	3	3	3	3
3000 A	3	3	3	3	3	3
4000 A	5	5	5	5	5	5
Permissible tripping delay Y seconds						
1200 A	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3
2000 A	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3
3000 A	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3	1 and 3
4000 A	1	1	1	1	1	1
Maximum voltage divided by K E/K kV rms ②	4.76	4.76	4.76	15.0	15.0	15.0
Current Values						
Maximum symmetrical interrupting capability						
Short-time current K x 1 kA rms ②	50	63	75	50	63	75
Closing and latching capability kA peak	137	173	206	137	173	206
Closing and latching momentary capability	82	103	123	82	103	123
Weight Lb (kg)						
1200 A	525 (238)	525 (238)	926 (419)	525 (238)	525 (238)	926 (419)
2000 A	530 (241)	530 (241)	936 (424)	530 (241)	530 (241)	936 (424)
3000 A	550 (250)	550 (250)	946 (429)	550 (250)	550 (250)	946 (429)
4000 A	956 (433)	956 (433)	956 (433)	956 (433)	956 (433)	956 (433)

Notes

① Applicable ANSI Standards C37.04-1999, C37.06-2000 (including both K >1 and K =1 ratings), C37.09-1999 and C37.013 (including C37.013a-2007).

② See *Consulting Application Guide* for further information.

Available Type VCP-W Vacuum Circuit Breakers Rated on Symmetrical Current Basis Per ANSI Standards (Rated K=1)

Identification	Drawout Circuit Breaker Type 50 VCP-W25	50 VCP-W40	50 VCP-W50	50 VCP-W63	75 VCP-W40	75 VCP-W50	150 VCP-W25	150 VCP-W40	150 VCP-W50	150 VCP-W63
Rated Values										
Maximum voltage (V) kV rms	4.76	4.76	4.76	4.76	8.25	8.25	15	15	15	15
Power frequency Hz ①	60	60	60	60	60	60	60	60	60	60
Insulation Level Power frequency withstand voltage (1 min.) kV rms	19	19	19	19	36	36	36	36	36	36
Lightning impulse withstand voltage (1.2 x 50 µs) kV peak	60	60	60	60	95	95	95	95	95	95
Continuous current A rms ②	1200	1200	1200	1200	1200	1200	1200 ⑩	1200	1200	1200 ⑩
	2000	2000	2000	2000	2000	2000	2000	2000	2000	2000 ⑩
	3000	3000	3000	3000	3000	3000	3000	3000	3000	3000 ⑩
Short-Circuit Ratings (Reference C37.04-1999 and C37.06-2009 except as noted ⑩) Symmetrical interrupting current (I) kA rms sym ③	25	40	50	63	40	50	25	40	50	63
DC component (% DC) ④	50	50	44	55	50	44	50	50	44	55
Asymmetrical interrupting current (I_t) kA rms asym total ⑤	31	49	59	80	49	59	31	49	59	80
Closing and latching current (2.6 x I) kA peak	65	104	130	164	104	130	65	104	130	164
Short-time withstand current rms ⑥	25	40	50	63	40	50	25	40	50	63
Transient Recovery Voltage parameters are based on TD-4 Peak voltage (E_2) = (u_c) (kV peak)	8.2	8.2	8.2	8.2	14	14	28 ⑩, 25.7	25.7	25.7	28 ⑩
Time to peak ($T_2 = t_3$ x 1.137) (µsec)	50	50	50	50	59	59	75	75	75	75
TRV rise time (t_3) (µsec)	44	44	44	44	52	52	66	66	66	66
RRRV = u_c/t_3 (kV/µsec) ⑦	0.19	0.19	0.19	0.19	0.27	0.27	0.42, 0.39	0.39	0.39	0.42
Interrupting time ms	50	50	50	50	50	50	50	50	50	50
Cycles (60 Hz)	3	3	3	3	3	3	3	3	3	3
Operating duty (duty cycle)	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO	O–0.3s–CO–3m–CO
Mechanical endurance no-load operations ⑧⑨	10,000	10,000	10,000	10,000	10,000	10,000	10,000	10,000	10,000	10,000

Notes

① All circuit breakers are tested at 60 Hz, however, they can also be applied at 50 Hz with no de-rating.

② 4000 A fan cooled rating is available for 3000 A circuit breakers.

③ Because the voltage range factor K=1, the short-time withstand current and the maximum symmetrical interrupting current are equal to the rated symmetrical interrupting current.

④ Based on the standard DC time constant of 45 ms (corresponding to X/R of 17 for 60 Hz) and the minimum contact parting time as determined from the minimum opening time plus the assumed minimum relay time of 1/2 cycle (8.33 ms for 60 Hz).

⑤ The asymmetrical interrupting current, I total, is given by (I_t) = I x Sqrt (1 + 2 x %DC x %DC) kA rms asym total.

⑥ Duration of short-time current and maximum permissible tripping delay are both 2 seconds for all circuit breakers listed in this table, as required in C37.04-1999, C37.06-2000 and C37.06-2009.

⑦ RRRV can also be calculated as = 1.137 x E_2/T_2.

⑧ Each operation consists of one closing plus one opening.

⑨ All 40 and 50 kA circuit breakers exceed required 5000 no-load operations; all 63 kA circuit breakers exceed the required 2000 no-load ANSI operations.

⑩ These circuit breakers were tested to the preferred TRV ratings specified in C37.06-2000.

Available Type VCP-W Vacuum Circuit Breakers Rated on Symmetrical Current Basis Per ANSI Standards (Rated K=1), continued

	Drawout Circuit Breaker Type									
Identification	**50 VCP-W25**	**50 VCP-W40**	**50 VCP-W50**	**50 VCP-W63**	**75 VCP-W40**	**75 VCP-W50**	**150 VCP-W25**	**150 VCP-W40**	**150 VCP-W50**	**150 VCP-W63**
Capacitance Current Switching Capability (Reference C37.04a-2003, C37.06-2009 and C37.09a-2005)										
Cable-charging current										
Class	C2	C2	C2	C2	C2	C2	C2	C2	C2	C2
A rms	3–10	3–10	3–10	7.5–25	7.5–25	7.5–25	7.5–25	7.5–25	7.5–25	7.5–25
Isolated shunt capacitor bank current										
Class	C2	C2	C2	C2	C2	C2	C2, C2, C1	C2, C2, C1	C2, C2, C1	C2
A rms										
1200 A	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630
2000 A	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000
3000 A	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600
Back-to-Back Capacitor Switching										
Capacitor bank current										
Class	C2	C2	C2	C2	C2	C2	C2, C2, C1	C2, C2, C1	C2, C2, C1	C2
A rms										
1200 A	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630	75–630
2000 A	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000	75–1000
3000 A	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600	75–1600
Inrush current kA peak	6	6	6	6	6	6	6	6	6	6
Inrush frequency kHz										
1200 A	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
2000 A	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
3000 A	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
Out-of-Phase Switching										
Voltage = 1.44 x V (kV rms)	7	7	7	7	12	12	22	22	22	22
Current = 0.25 x I (kA rms)	6.3	10	12.5	15.8	10	12.5	6.3	10	12.5	15.8

VCP-W Vacuum Breaker Types Rated on Symmetrical Current Rating Basis ①

	Circuit Breaker Type							
	270 VCP-W750	**270 VCP-W1000**	**270 VCP-W1250**	**270 VCP-W1600**	**270 VCP-W2000**	**270 VCP-W25C**	**270 VCP-W32C**	**270 VCP-W40C**
Identification								
Nominal voltage class kV	27	27	27	27	27	27	27	27
Nominal three-phase MVA class	750	1000	1250	1600	2000	—	—	—
Rated Values								
Voltage								
Maximum voltage E kV rms	27 ②	27 ②	27 ②	27 ②	27 ②	27	27	27
Voltage range factor K ③	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
Insulation Level								
Withstand test voltage								
Power frequency (1 min.) kV rms	60	60	60	60	60	60	60	60
Impulse kV peak	125	125	125	125	125	125	125	125
Current								
Continuous current at 60 Hz amperes	600	600	600	1200	1200	1200	1200	1200
	1200	1200	1200	2000	2000	1600	1600	1600
	2000	2000	2000	—	—	—	—	—
Short-circuit current (at rated maximum kV) ④⑤	16	22	25	25	40	25 ⑦	31.5 ⑧	40 ⑨
Interrupting time ms (cycles)	83 (5) ⑥	83 (5) ⑥	83 (5) ⑥	83 (5) ⑥	83 (5) ⑥	50 (3)	50 (3)	50 (3)
Maximum permissible tripping delay Y seconds	2	2	2	2	2	2.5	1.6	1.0
Transient recovery voltage E_2 kV peak	51	51	51	51	51	50	50	50
T_2 µs	105	105	105	105	105	50	50	50
Current Values								
Closing and latching capability (2.6 K times rated short-circuit current) kA peak	43	60	68	85	106	85	100	112
Capacitor switching cable charging amperes	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5
Weight Lb (kg)								
600 A	460 (209)	460 (209)	460 (209)	545 (247)	545 (247)	545 (247)	545 (247)	545 (247)
1200 A	480 (218)	480 (218)	480 (218)	560 (254)	600 (272)	560 (254)	560 (254)	560 (254)
2000 A	500 (227)	500 (227)	500 (227)	—	—	—	—	—

Notes

① CESI tested to applicable ANSI standards C37.04, C37.09 and C37.06. Consult Eaton for CESI copies of test reports on file. Operating duty cycle CO-15 seconds-CO. Operating time values: Opening 33–55 ms, closing 50–60 ms and reclosing 18 cycles (300 ms).

② Tested at 28.5 kV.

③ K = 1.0, therefore E = E/K and I = KI.

④ Also maximum interruption rating and short-time current rating.

⑤ Duration of short-time current = 3 seconds, except as noted in footnotes 7, 8 and 9.

⑥ Optional interrupting time of 50 ms (3 cycles) is available.

⑦ Duration of short-time current = 2.5 seconds.

⑧ Duration of short-time current = 1.6 seconds.

⑨ Duration of short-time current = 1 second.

Type VCP-W Vacuum Circuit Breaker Ratings

Type VCP-W Ratings on Symmetrical Current Rating Basis ①②

Identification	Circuit Breaker Type 380 VCP-W 6 and 380 VCP-WR 16	380 VCP-W 25 and 380 VCP-WR 25	380 VCP-W 32 and 380 VCP-WR 32	380 VCP-W 21 and 380 VCP-WR 21	380 VCP-W 40 and 380 VCP-WR 40
Rated Values					
Voltage					
Nominal voltage class kV rms	34.5	34.5	34.5	34.5	34.5
Maximum voltage V kV rms	38	38	38	38	38
Voltage range factor K ③	1	1	1	1.65 ⑧	1
V/K ③ kV rms	38	38	38	23 ⑧	38
Insulation Level Withstand Test					
Power frequency (1 minute) kV rms	80	80	80	80	80
Lightning impulse 1.2 x 50 ④ kV peak	170	170	170	170	170
Current					
Continuous current at 60 Hz ⑤ A rms	600	600	600	1200	1200
	1200	1200	1200	2000	2000
	1600	1600	1600	3000FC	3000FC
	2000	2000	2000	2500	2500
	—	—	3000FC	—	—
	—	—	2500	—	—
Short-Circuit Current					
Sym. interrupting at V (Isc) kA rms	16	25	31.5	21	40
% DC component (Idc)	47	47	47	47	47
Asym. factor S (ref.)	1.2	1.2	1.2	1.2	1.2
Asym. interrupting (I_t) kA rms total	19.2	30.0	37.8	39.5	48.0
Maximum asym. interrupting at V/K (KxIsc) ③ kA rms	16	25	31.5	35 ⑧	40
Maximum asym. interrupting at V/K (SxKxIsc) ③ kA rms total	19.3	30.0	37.8	42.0	48.0
Closing and latching capability kA peak	43	68	85	95	107
Momentary current withstand capability kA rms total	26	40	50	56	63
Short-time current kA rms	16	25	31.5	35	40
Duration of short-time current s	3	3	3	3	3
Operating duty (duty cycle)	⑨⑩	⑨⑩	⑨⑩ (2500 only ⑨⑪)	⑨⑩ (2500 only ⑨⑪)	⑨⑪
Rated reclosing factor (R) %	100	100	100 (2500 only 0%)	100 (2500 only 0%)	100
Interrupting time ⑥ rms	83	83	83	83	83
Cycle	5	5	5	5	5
Maximum permissible tripping delay sec.	2	2	2	2	2
Transient recovery voltage (RRRV) kV/µs	0.6	0.6	0.6	0.6	0.6
Mechanical endurance ⑦	2000	2000	2000	2000	2000

Notes

① KEMA tested to applicable ANSI standards C37.04-1979, C37.09-1979 and C37.06-1979 (operating duty sequence CO–15s–CO). Typical operating time values: operating 45 ms, closing 75 ms and reclosing 300 ms (18 cycles).

② The standard breaker is not rated for capacitor switching. If you require capacitor switching, please refer to the "C" breakers.

③ K = 1.0, therefore E = E/K and I = KI. Refer to the *Consulting Application Guide* for more information.

④ The ANSI C37.06 standard requires 150 kV BIL. If higher BIL levels are required, please refer to the "C" breakers.

⑤ For forced air cooled fixed breaker applications, consult Eaton.

⑥ If you require 50 ms (3 cycle) interrupting time, please refer to the "C" breakers.

⑦ No-load operations.

⑧ At 23 kV rms (rated maximum voltage/K). Rated maximum symmetrical interrupting capability = 35 kA rms (K x 1).

⑨ CO–15s–CO.

⑩ Rated and tested also for rapid reclosing capability O–0.3s–CO.

⑪ Not rated for rapid reclosing.

Type VCP-WC Vacuum Circuit Breaker Ratings

Type VCP-WC Ratings on Symmetrical Current Rating Basis ①②

Identification	Drawout Circuit Breaker Type 380 VCP-W 16C and 380 VCP-WR 16C	380 VCP-W 25C and 380 VCP-WR 25C	380 VCP-W 32C and 380 VCP-WR 32C	380 VCP-W 21C and 380 VCP-WR 21C	380 VCP-W 40C and 380 VCP-WR 40C
Rated Values					
Voltage					
Nominal voltage class kV rms	34.5	34.5	34.5	34.5	34.5
Maximum voltage V kV rms	38	38	38	38	38
Voltage range factor K ③	1	1	1	1.65 ⑧	1
V/K ③ kV rms	38	38	38	23 ⑧	38
Insulation Level Withstand Test					
Power frequency (1 minute) kV rms	80	80	80	80	80
Lightning impulse 1.2 x 50 µs ④ kV peak	170	170	170	170	170
Current					
Continuous current at 60 Hz ⑤ A rms	600	600	600	1200	1200
	1200	1200	1200	2000	2000
	1600	1600	1600	3000FC	3000FC
	2000	2000	2000	2500	2500
	—	—	3000FC	—	—
	—	—	2500	—	—
Short-Circuit Current					
Sym. interrupting at V (Isc) kA rms	16	25	33.1	21	40
% DC component (Idc)	75	65	57	52	63
Asym. factor S (ref.)	1.46	1.36	1.3	1.24	1.34
Asym. interrupting (I_t) kA rms total	23.3	34.0	42.5	26.1	53.5
Maximum sym. interrupting at V/K (KxIsc) ③ kA rms	16	25	33.1	35 ⑧	40
Maximum asym. interrupting at V/K (SxKxIsc) ③ kA rms total	23.3	34.0	42.5	43.4	53.5
Closing and latching capability kA peak	50	75	91	102	107
Momentary current withstand capability kA rms total	30	44	54	60	65
Short-time current kA rms	16	25	31.5	35	40
Duration of short-time current s	3.09	3.09	3.09	3.21	3.04
Operating duty (duty cycle)	⑨⑩	⑨⑩	⑨⑩ (2500 A ⑪)	⑨⑩ (2500 A ⑪)	⑨⑪
Rapid reclosing factor (R) %	100	100	100 (2500 A N/A)	100 (2500 A N/A)	—
Interrupting time ⑥ rms	50	50	50	50	50
Cycles	3	3	3	3	3
Maximum permissible tripping delay sec.	2	2	2	2	2
Transient recovery voltage (RRRV) kV/µs	0.7	0.7	0.7	0.7	—
	1.3	1.3	0.7	1.3	—
	—	—	0.7	1.3	—
	—	—	1.3	0.7	—
	—	—	1.3	—	—
	—	—	0.7	—	—

Notes

① KEMA tested to applicable ANSI standards C37.04-1979, C37.09-1979 and C37.06-1979 (operating duty sequence CO–15s–CO). Typical operating time values: operating 45 ms, closing 75 ms and reclosing 300 ms (18 cycles).

② The standard breaker is not rated for capacitor switching. If you require capacitor switching, please refer to the "C" breakers.

③ K = 1.0, therefore E = E/K and I = KI. Refer to the *Consulting Application Guide* for more information.

④ The ANSI C37.06 standard requires 150 kV BIL. If higher BIL levels are required, please refer to the "C" breakers.

⑤ For forced air cooled fixed breaker applications, consult Eaton.

⑥ If you require 50 ms (3 cycle) interrupting time, please refer to the "C" breakers.

⑦ No-load operations.

⑧ At 23 kV rms (rated maximum voltage/K). Rated maximum symmetrical interrupting capability = 35 kA rms (K x 1).

⑨ CO–15s–CO.

⑩ Rated and tested also for rapid reclosing capability O–0.3s–CO.

⑪ Not rated for rapid reclosing.

Type VCP-WC Vacuum Circuit Breaker Ratings

Type VCP-WC Ratings on Symmetrical Current Rating Basis, continued①②

Identification	Drawout Circuit Breaker Type 380 VCP-W 16C and 380 VCP-WR 16C	380 VCP-W 25C and 380 VCP-WR 25C	380 VCP-W 32C and 380 VCP-WR 32C	380 VCP-W 21C and 380 VCP-WR 21C	380 VCP-W 40C and 380 VCP-WR 40C
Capacitor Switching Ratings					
Definite Purpose					
Overhead line current A rms	5	5	5 (2500 A N/A)	5 (2500 A N/A)	—
Isolated shunt capacitor bank current A rms	250	250	250	250	—
	250 and 1000 (2000 A)	250 and 1000 (2000 A)	250 and 1000 (2000 A and 3000FC) (2500 N/A)	250 and 1000 (2000 A and 3000FC) (2500 N/A)	—
Definite Purpose—Back-to-Back Capacitor Switching					
Cable charging current A rms	56	56	53	53	53
Capacitor bank current A rms	250	250	250	250	—
	250 and 1000 (200 A)	250 and 1000 (200 A)	250 and 1000 (2000 A and 3000FC) (2500 N/A)	250 and 1000 (2000 A and 3000FC) (2500 N/A)	—
Inrush current kA peak	20	20	20	20	—
	20 and 20 (2000 A)	20 and 20 (2000 A)	20 and 20 (2000 A and 3000FC) (2500 N/A)	20 and 20 (2000 A and 3000FC) (2500 N/A)	—
Inrush frequency kHz	4.4	4.4	4.4	4.4	—
	5 and 5 (2000 A)	5 and 5 (2000 A)	5 and 5 (2000 A and 3000FC) (2500 N/A)	5 and 5 (2000 A and 3000FC) (2500 N/A)	—
Mechanical endurance (no-load operations)	15,000	15,000	15,000	15,000	15,000

3

IEC Standards

IEC Standards ①—VCP-W Vacuum Circuit Breaker Types Rated on Symmetrical Current Rating Basis

Identification	Rated Values							
		Insulation Level			Short-Circuit Breaking Current and 3-Second Short-Time Current	Short-Circuit Making Current	Cable Charging Breaking Current	
Circuit Breaker Type	Voltage kV rms	Power Frequency kV rms Peak	Impulse Withstand kV Peak	Normal Current Amperes	kA rms	kV Peak	Amperes	Weight Lb (kg)
36 VCP-WND25	3.6	10	40	630	25	65	10	350 (159)
	3.6	10	40	1250	25	65	10	350 (159)
36 VCP-WND32	3.6	10	40	630	31.5	82	10	350 (159)
	3.6	10	40	1250	31.5	82	10	350 (159)
72 VCP-WND25	7.2	20	60	630	25	65	10	350 (159)
	7.2	20	60	1250	25	65	10	350 (159)
72 VCP-WND32	7.2	20	60	630	31.5	82	10	350 (159)
	7.2	20	60	1250	31.5	82	10	350 (159)
36 VCP-W25	3.6	10	40	630	25	65	10	414 (188)
	3.6	10	40	1250	25	65	10	430 (195)
	3.6	10	40	2000	25	65	10	496 (225)
36 VCP-W32	3.6	10	40	1250	31.5	82	10	414 (188)
	3.6	10	40	2000	31.5	82	10	496 (225)
36 VCP-W40	3.6	10	40	1250	40	104	10	496 (225)
	3.6	10	40	2000	40	104	10	550 (250)
72 VCP-W25	7.2	20	60	630	25	65	10	414 (188)
	7.2	20	60	1250	25	65	10	414 (188)
	7.2	20	60	2000	25	65	10	496 (225)
72 VCP-W32	7.2	20	60	1250	31.5	82	10	414 (188)
	7.2	20	60	2000	31.5	82	10	430 (195)
72 VCP-W40	7.2	20	60	1250	40	104	10	430 (195)
	7.2	20	60	2000	40	104	10	496 (225)
120 VCP-W25	12.0	28	75	630	25	65	25	430 (195)
	12.0	28	75	1250	25	65	25	496 (225)
	12.0	28	75	2000	25	65	25	496 (225)
120 VCP-W32	12.0	28	75	1250	31.5	82	25	430 (195)
	12.0	28	75	2000	31.5	82	25	496 (225)
120 VCP-W40	12.0	28	75	1250	40	104	25	496 (225)
	12.0	28	75	2000	40	104	25	550 (250)
175 VCP-W25	17.5	38	95	630	25	65	—	430 (195)
	17.5	38	95	1250	25	65	—	496 (225)
	17.5	38	95	2000	25	65	—	496 (225)
175 VCP-W32	17.5	38	95	1250	31.5	82	—	430 (195)
	17.5	38	95	2000	31.5	82	—	496 (225)
175 VCP-W40	17.5	38	95	1250	40	104	—	496 (225)
	17.5	38	95	2000	40	104	—	550 (250)
175 VCP-W50	17.5	38	95	1250	50	130	—	1013 (460)
	17.5	38	95	2000	50	130	—	1079 (490)
	17.5	38	95	3150	50	130	—	1156 (525)

Note

① IEC Standards 60056 and 60694 apply.

ANSI Standard Ratings—VCP-T and VCP-TR Vacuum Circuit Breakers (to ANSI C37.04 and C37.09)

Identification	Rated Values						
		Insulation Level					
Circuit Breaker Type	Voltage Class	Power Frequency	Impulse Withstand	Continuous Current	Short-Circuit ③ Breaking Current	Short-Circuit Making Current	Mechanical Endurance C–O
	kV rms	kV rms	kV Peak	Amperes	kA rms	kA Peak	Operations
50 VCP-T16 and 50 VCP-TR16	4.76	19	60	600	16	42	20,000
	4.76	19	60	800	16	42	20,000
	4.76	19	60	1200	16	42	10,000
	4.76	19	60	1600 ②	16	42	10,000
50 VCP-T20 and 50 VCP-TR20	4.6	19	60	600	16	52	10,000
	4.6	19	60	800	16	52	10,000
	4.6	19	60	1200	16	52	10,000
	4.6	19	60	1600 ②	16	52	10,000
50 VCP-T25 and 50 VCP-TR25	4.76	19	60	600	25	65	10,000
	4.76	19	60	800	25	65	10,000
	4.76	19	60	1200	25	65	10,000
	4.76	19	60	1600 ②	25	65	10,000
75 VCP-T16 and 75 VCP-TR16	8.25	20	60 ①	600	16	42	20,000
	8.25	20	60 ①	800	16	42	20,000
	8.25	20	60 ①	1200	16	42	10,000
	8.25	20	60 ①	1600 ②	16	42	10,000
75 VCP-T20 and 75 VCP-TR20	8.25	20	60 ①	600	20	52	10,000
	8.25	20	60 ①	800	20	52	10,000
	8.25	20	60 ①	1200	20	52	10,000
	8.25	20	60 ①	1600 ②	20	52	10,000
75 VCP-T25 and 75 VCP-TR25	8.25	20	60 ①	600	25	65	10,000
	8.25	20	60 ①	800	25	65	10,000
	8.25	20	60 ①	1200	25	65	10,000
	8.25	20	60 ①	1600 ②	25	65	10,000
150 VCP-T16 and 150 VCP-TR16	15	36	95	600	16	42	10,000
	15	36	95	800	16	42	10,000
	15	36	95	1200	16	42	10,000
	15	36	95	1600 ②	16	42	10,000
150 VCP-T20 and 150 VCP-TR20	15	36	95	600	20	52	10,000
	15	36	95	800	20	52	10,000
	15	36	95	1200	20	52	10,000
	15	36	95	1600 ②	20	52	10,000
150 VCP-T25 and 150 VCP-TR25	15	36	95	600	25	65	10,000
	15	36	95	800	25	65	10,000
	15	36	95	1200	25	65	10,000
	15	36	95	1600 ②	25	65	10,000

Notes

① Use 15 kV breaker and cassette when 95 kV impulse withstand required.

② 1600 A VCP-T breaker available.

③ Also 2 second short-time current rating.

ANSI Standard Ratings—VCP-TL/VCP-TRL Vacuum Circuit Breakers (to ANSI C37.04 and C37.09)

Identification	Rated Values							
		Insulation Level						
Circuit Breaker Type ①	Rated Maximum Voltage kV rms	Power Frequency kV rms	Impulse Withstand kV Peak	Continuous Current Amperes	Short-Circuit Breaking Current ② kA rms	Short-Circuit Making Current kA Peak	Mechanical Endurance ③ C–O Operations	Approx. Weight Fix/Drawout Lb
50 VCP-TL16 and 50 VCP-TRL16	4.76	19	60	600	16	42	100,000	153/232
				1200	16	42	100,000	155/234
				1600 ④	16	42	100,000	157/NA
50 VCP-TL20 and 50 VCP-TRL20	4.76	19	60	600	20	52	100,000	159/237
				1200	20	52	100,000	161/239
				1600 ④	20	52	100,000	163/NA
50 VCP-TL25 and 50 VCP-TRL25	4.76	19	60	600	25	65	100,000	166/243
				1200	25	65	100,000	168/245
				1600 ④	25	65	100,000	170/NA
75 VCP-TL16 and 75 VCP-TRL16	8.25	20	75 ⑤	600	16	42	100,000	155/232
				1200	16	42	100,000	157/234
				1600 ④	16	42	100,000	159/NA
75 VCP-TL20 and 75 VCP-TRL20	8.25	20	75 ⑤	600	20	52	100,000	161/239
				1200	20	52	100,000	161/241
				1600 ④	20	52	100,000	163/NA
75 VCP-TL25 and 75 VCP-TRL25	8.25	20	75 ⑤	600	25	65	100,000	166/245
				1200	25	65	100,000	168/247
				1600 ④	25	65	100,000	170/NA
150 VCP-TL16 and 150 VCP-TRL16	15	36	95	600	16	42	100,000	155/234
				1200	16	42	100,000	157/237
				1600 ④	16	42	100,000	159/NA
150 VCP-TL20 and 150 VCP-TRL20	15	36	95	600	20	52	100,000	161/239
				1200	20	52	100,000	163/241
				1600 ④	20	52	100,000	166/NA
150 VCP-TL25 and 150 VCP-TRL25	15	36	95	600	25	65	100,000	168/245
				1200	25	65	100,000	170/247
				1600 ④	25	65	100,000	172/NA

Notes

① Independent shunt trips are available for use with traditional protective relaying schemes.

② Also 2-second short-time current rating.

③ Operating mechanism up to 100,000 operations, vacuum interrupter 30,000.

④ 1600 A available as fixed VCP-TRL/VCP-TRLC circuit breaker only.

⑤ Use 15 kV breaker and cassette when impulse withstand >75 kV is required.

IEC Standard Ratings—T-VAC and T-VACR Vacuum Circuit Breakers (to IEC 62271-100)

Identification	Rated Values						
		Insulation Level					
Circuit Breaker Type	Voltage Class	Power Frequency Withstand Voltage	Lightning Impulse (U_w) Withstand Voltage	Normal Current (I_n)	Short-Circuit ③ Breaking Current	Short-Circuit Making Current	Mechanical Endurance C–O
	kV rms	kV rms	kV Peak	Amperes	kA rms	kA Peak	Operations
72 T-VAC16 and 72 T-VACR16	7.2	20	60	630	16	40	20,000
	7.2	20	60	800	16	40	20,000
	7.2	20	60	1250	16	40	10,000
	7.2	20	60	1600 ②	16	40	10,000
72 T-VAC20 and 72 T-VACR20	7.2	20	60	630	20	50	10,000
	7.2	20	60	800	20	50	10,000
	7.2	20	60	1250	20	50	10,000
	7.2	20	60	1600 ②	20	50	10,000
72 T-VAC25 and 72 T-VACR25	7.2	20	60	630	25	63	10,000
	7.2	20	60	800	25	63	10,000
	7.2	20	60	1250	25	63	10,000
	7.2	20	60	1600 ②	25	63	10,000
120 T-VAC16 and 120 T-VACR16	12	28	75 ①	630	16	40	20,000
	12	28	75 ①	800	16	40	20,000
	12	28	75 ①	1250	16	40	10,000
	12	28	75 ①	1600 ②	16	40	10,000
120 T-VAC20 and 120 T-VACR20	12	28	75 ①	630	20	50	10,000
	12	28	75 ①	800	20	50	10,000
	12	28	75 ①	1250	20	50	10,000
	12	28	75 ①	1600 ②	20	50	10,000
120 T-VAC25 and 120 T-VAC25	12	28	75 ①	630	25	63	10,000
	12	28	75 ①	800	25	63	10,000
	12	28	75 ①	1250	25	63	10,000
	12	28	75 ①	1600 ②	25	63	10,000
175 T-VAC16 and 175 T-VACR16	17.5	38	95	630	16	40	10,000
	17.5	38	95	800	16	40	10,000
	17.5	38	95	1250	16	40	10,000
	17.5	38	95	1600 ②	16	40	10,000
175 T-VAC20 and 175 T-VACR20	17.5	38	95	630	20	50	10,000
	17.5	38	95	800	20	50	10,000
	17.5	38	95	1250	20	50	10,000
	17.5	38	95	1600 ②	20	50	10,000
175 T-VAC25 and 175 T-VACR25	17.5	38	95	630	25	63	10,000
	17.5	38	95	800	25	63	10,000
	17.5	38	95	1250	25	63	10,000
	17.5	38	95	1600 ②	25	63	10,000

Notes

① Use 17.5 kV breaker and cassette when 95 kV impulse withstand required.

② 1600 A T-VAC breaker available.

③ Also 3-second short-time current rating.

Dimensions

Approximate Dimensions in Inches (mm)

Type VCP-W Circuit Breaker Shown from Rear



Type VCP-W Circuit Breaker with Deadfront Panel Removed

Mini Module

5/15 kV VCPW-ND and VCP-W Power Modules

Power Module, 5/15 kV VCPW-ND 26.00 (660.4) Wide, VCP-W 36.00 (914.4) Wide



Note

① VCPW-ND dimensions of breaker travel 15.00 (381.0).

Approximate Dimensions in Inches (mm)

5/15 kV VCPW-ND and VCP-W Mini Modules

5 kV VCPW-ND Mini Module 25.88 (657.4) Wide



5/15 kV VCP-W Mini Module

5/15 kV VCP-W Mini-Module 35.88 (911.4) Wide



Note

① Current transformers not supplied.

Contents

Description	*Page*
Catalog Number Selection	**V4-T3-73**
SL MV Power Contactor 7.2 kV/160–400A	**V4-T3-74**
SL MV Power Contactor 7.2 kV/800A	**V4-T3-83**
SL MV Power Contactor 15 kV/300A	**V4-T3-87**

Product Overview

Voltage Class

Eaton SL Medium Voltage Vacuum Contactors are designed to operate at voltages from 2200V to 15,000V, depending on contactor type. Typical system voltages are 2400V, 3300V, 4160V and 6600V for 7.2 kV contactors and 10,000V, 11,000V, 13,200V and 13,800V for 15 kV contactors.

Altitude

7.2 kV/160–400A SL Contactors are capable of operating in virtually any altitude range. Three versions are offered in Standard, High and Low altitude configurations. No de-rating is necessary for proper operation. Altitude designations are listed in the table below.

Altitude

Altitude	Low	Standard	High
7.2 kV/160–400A			
Feet	–11,500 to –3300	–3300 to +6600	+6600 to +13,100
Meters	–3500 to –1000	–1000 to +2000	+2000 to +4000
7.2 kV/800A and 15 kV/300A			
Feet	N/A	–3300 to +11,800	+11,800 to +16,000
Meters	N/A	–1000 to +3600	+3600 to +4900

Control Voltage and Dropout Time

Control coil voltage and dropout time for all SL contactors are field selectable. Standard voltages available are 120/60V, 110/50V, 240/60V, 220/50V and 125 Vdc. Coil will pick up at 80% of rated coil voltage and dropout not sooner than 60% of rated coil voltage. Opening time is field selectable within the range of 30–330 ms for all 7.2 kV 160–400A contactors. Opening time is field selectable within the range of 50–330 ms for all 7.2 kV 800A and 15 kV 300A contactors.

Catalog Number Selection

Power Contactors

SL N 01 2 S 5 A - 22 0

SL Contactor Series

Design

N = NEMA
C = IEC

Type

01 = 7.2 kV (160–400A) Contactor
03 = 15 kV (300A) Contactor
04 = 7.2 kV (800A) Contactor

Ampere Rating

1 = 160A
2 = 7.2 kV/200A
3 = 7.2 kV/360A, 15 kV/300A
4 = 400A
8 = 800A

Altitude

7.2 kV/160–400A	7.2 kV/800A 15 kV/300A
S = Standard –3281 to +6562 ft (–1000 to +2000m) **L** = Low –11,483 to –3281 ft (–3500 to –1000m) **H** = High +6562 to +13,123 ft (+2000 to +4000m)	**S** = Standard –3281 to +11,811 ft (–1000 to +3600m) **H** = High +11,811 to +16,076 ft (+3600 to +4900m)

Coil Dropout Time

5 = 30 ms 7.2 kV (160–400A)
6 = 50 ms
7 = 130 ms
8 = 250 ms
9 = 330 ms

Coil Voltage

A = 120/60
B = 240/60
S = 125 Vdc
U = 110/50
W = 220/50

Auxiliary Contacts

7.2 kV/160–400A	7.2 kV/800A 15 kV/300A
22 = 2NO, 2NC **28** = 2NO, 8NC **37** = 3NO, 7NC **46** = 4NO, 6NC **55** = 5NO, 5NC **64** = 6NO, 4NC **73** = 7NO, 3NC **82** = 8NO, 2NC	**22** = 2NO, 2NC

Mechanical Latch

7.2 kV/160–400A (Coil Voltage)	7.2 kV/800A 15 kV/300A (Coil Voltage)
0 = None **1** = 24 Vdc **2** = 32 Vdc **3** = 48 Vdc **4** = 110/50,120/60 or 125 Vdc **5** = 220/50, 240/60	**0** = None **1** = 24 Vdc **3** = 48 Vdc **4** = 110 (50/60) **5** = 220 (50/60) **6** = 96–125 Vdc

SL 7.2 kV/160–400A Medium Voltage Contactor

Contents

Description	*Page*
Product Overview	**V4-T3-72**
SL MV Power Contactor 7.2 kV/160–400A	
Standards and Certifications	**V4-T3-76**
Product Selection	**V4-T3-76**
Options and Accessories	**V4-T3-76**
Technical Data and Specifications	**V4-T3-77**
Wiring Diagrams	**V4-T3-80**
Dimensions	**V4-T3-81**
SL MV Power Contactor 7.2 kV/800A	**V4-T3-83**
SL MV Power Contactor 15 kV/300A	**V4-T3-87**

SL MV Power Contactor 7.2 kV/160–400A

Product Description

- A single family of contactors for any medium voltage control application. Voltage range of 2200–7200V
- Ampere ratings from 160 to 400A with induction motor horsepower ranges from 600 to 5500 hp
- Three different altitude versions
- Leading-edge vacuum technology
- Fully complies with global standards

Application Description

Eaton's SL Medium Voltage Contactor starting applications:

- Squirrel-cage induction motors
- Synchronous motors
- Wound-rotor

Fully applicable to:

- Full voltage starting
- Reduced voltage starting

The perfect choice for harsh duty applications:

- Mining
- Pulp and paper
- HVAC
- Petrochemical
- Automotive
- Many others

Features, Benefits and Functions

- Long life—300,000 electrical and over 2 million mechanical
- Mounting flexibility—panel or pedestal mounting provisions are standard. Unit can be mounted in horizontal or vertical position
- Field-selectable settings for coil voltage, AC/DC, and coil dropout time
- Field kits available for auxiliary contacts and mechanical latch. Accessories are common for all sizes
- Special ordering allows unit to be factory pre-set to customer specification, including field kit installation
- Highest quality available—all contactors manufactured within state-of-the-art "ISO-Certified" facilities. 100% made in America

Easy-to-Install Option Kits (Field Addition)

- Up to six extra auxiliary contacts
- Mechanical latch—many coil voltages

SL Series Features (7.2 kV/160–400A)



Control Settings

Control Terminal Strip



Coil Control Board



DIP Switches

Standards and Certifications

Global Acceptability

- NEMA
- ANSI
- IEC

Third-Party Verification

- UL
- CSA
- KEMA
- Third-party qualified by UL, CSA, KEMA

Design and Test Standards

- UL 347, File No. E63257
- CSA File No. LR28548
- IEC No. 60470
- ANSI/NEMA ICS 3

Product Selection

Contact Eaton for pricing.

Options and Accessories

SL Vacuum Contactor Series—Sizes 7.2 kV/160–400A Accessory Kits

Mechanical Latch Kit

Field Mount to 7.2 kV/160–400A SL Vacuum Contactor. Coil voltages available in a wide range of AC and DC selections. Easy to install on new and existing units.

Mechanical Latch Kit

Ordering Information—Mechanical Latch Kit

Coil Voltage	Catalog Number
24 Vdc	**SLA-ML24**
32 Vdc	**SLA-ML32**
48 Vdc	**SLA-ML48**
110/50, 120/60, 125 Vdc selectable	**SLA-ML120**
220/50, 240/60 selectable	**SLA-ML240**

Auxiliary Contact Kit

Field Mount auxiliary contact kits for 7.2 kV/160–400A SL Vacuum Contactor. Contact kits are available in many configurations of NO-NC.

Auxiliary Contact Kit

Ordering Information—Auxiliary Contact Kit

Description	Catalog Number
3NO–3NC additional	**SLA-AS33**
6NO additional	**SLA-AS60**
6NC additional	**SLA-AS06**
5NO–1NC additional	**SLA-AS51**
4NO–2NC additional	**SLA-AS42**
2NO–4NC additional	**SLA-AS24**
1NO–5NC additional	**SLA-AS15**

Mechanical Interlock Kit

Field Mount mechanical interlock kits for 7.2 kV/160–400A SL Vacuum Contactor.

Mechanical Interlock Kit

Ordering Information—Mechanical Interlock Kit

Description	Catalog Number
Vertical or horizontal arrangement	**SLA-MI**

Technical Data and Specifications

The SL 400 Contactor Ratings

- Voltages of 2200–7200V
- Amperages from 160 to 400A
- Interrupting ratings as high as 8500A

Control Voltages (Field Adjustable)

- 110, 220 Vac, 50 Hz
- 120, 240 Vac, 60 Hz
- 125 Vdc

Dropout Time (Field Adjustable)

- 30 ms
- 50 ms
- 130 ms
- 250 ms
- 330 ms

Front and Rear View (7.2 kV/160–400A)

Front View

Rear View

Control Voltage Settings (7.2 kV/160–400A)

Setting	SW1	SW2	SW3
110 Vac, 50 Hz	Off	Off	Off
120 Vac, 60 Hz	On	Off	Off
220 Vac, 50 Hz	Off	On	Off
240 Vac, 60 Hz	On	On	Off
125 Vdc	Off	Off	On

Dropout Time Settings (7.2 kV/160–400A)

Delay Setting	SW4	SW5	SW6
30 ms	Off	Off	Off
50 ms	On	Off	Off
130 ms	Off	On	Off
250 ms	On	On	Off
330 ms	Off	Off	On

Altitude Designations (7.2 kV/160–400A)

Altitude	Low	Standard	High
Feet	–11,483 to –3281	–3281 to +6562	+6562 to +13,123
Meters	–3500 to –1000	–1000 to +2000	+2000 to +4000

Note

Stock units pre-set to 120/60 Vac.

SL Series Fuses

Fuse Application Table for SL Contactors—7.2 kV/160A

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
11–18	2400–4800	5BCLS-30	30–1R	30
18–31	2400–4800	5BCLS-2R	70–2R	30
31–46	2400–4800	5BCLS-3R	100–3R	30
46–62	2400–4800	5BCLS-4R	130–4R	30
62–74	2400–4800	5BCLS-5R	150–5R	30
74–93	2400–4800	5BCLS-6R	170–6R	30
93–137	2400–4800	5BCLS-9R	200–9R	130
137–160	2400–4800	5BCLS-12R	230–12R	130
11–34	5500–6600	7BCLS-2R	70–2R	30
34–46	5500–6600	7BCLS-3R	100–3R	30
46–56	5500–6600	7BCLS-4R	130–4R	30
56–68	5500–6600	7BCLS-5R	150–5R	30
68–85	5500–6600	7BCLS-6R	170–6R	30
85–137	5500–6600	7BCLS-9R	200–9R	50
137–160	5500–6600	7BCLS-12R	230–12R	250

Fuse Application Table for SL Contactors—7.2 kV/200A

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
11–18	2400–4800	5BCLS-30	30–1R	30
18–31	2400–4800	5BCLS-2R	70–2R	30
31–46	2400–4800	5BCLS-3R	100–3R	30
46–62	2400–4800	5BCLS-4R	130–4R	30
62–74	2400–4800	5BCLS-5R	150–5R	30
74–93	2400–4800	5BCLS-6R	170–6R	30
93–137	2400–4800	5BCLS-9R	200–9R	130
137–200 ①	2400–4800	5BCLS-12R	230–12R	130
11–34	5500–6600	7BCLS-2R	70–2R	30
34–46	5500–6600	7BCLS-3R	100–3R	30
46–56	5500–6600	7BCLS-4R	130–4R	30
56–68	5500–6600	7BCLS-5R	150–5R	30
68–85	5500–6600	7BCLS-6R	170–6R	30
85–137	5500–6600	7BCLS-9R	200–9R	50
137–200 ①	5500–6600	7BCLS-12R	230–12R	250

Fuse Application Table for SL Contactors—7.2 kV/360A

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
11–18	2400–4800	5BCLS-30	30–1R	30
18–31	2400–4800	5BCLS-2R	70–2R	30
31–46	2400–4800	5BCLS-3R	100–3R	30
46–62	2400–4800	5BCLS-4R	130–4R	30
62–74	2400–4800	5BCLS-5R	150–5R	30
74–93	2400–4800	5BCLS-6R	170–6R	30
93–137	2400–4800	5BCLS-9R	200–9R	130
137–187	2400–4800	5BCLS-12R	230–12R	130
187–200	2400–4800	5BCLS-12R	230–12R	130
200–360	2400–4800	N/A	—	—
11–34	5500–6600	7BCLS-2R	70–2R	30
34–46	5500–6600	7BCLS-3R	100–3R	30
46–56	5500–6600	7BCLS-4R	130–4R	30
56–68	5500–6600	7BCLS-5R	150–5R	30
68–85	5500–6600	7BCLS-6R	170–6R	30
85–137	5500–6600	7BCLS-9R	200–9R	50
137–200 ①	5500–6600	7BCLS-12R	230–12R	250
200–360	5500–6600	N/A	—	—

Fuse Application Table for SL Contactors—7.2 kV/400A

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
11–18	2400–4800	5BCLS-30	30–1R	30
18–31	2400–4800	5BCLS-2R	70–2R	30
31–46	2400–4800	5BCLS-3R	100–3R	30
46–62	2400–4800	5BCLS-4R	130–4R	30
62–74	2400–4800	5BCLS-5R	150–5R	30
74–93	2400–4800	5BCLS-6R	170–6R	30
93–137	2400–4800	5BCLS-9R	200–9R	30
137–187	2400–4800	5BCLS-12R	230–12R	30
187–273	2400–4800	5BCLS-18R	390–18R	50
273–400 ②	2400–4800	5BCLS-24R	450–24R	130
11–34	5500–6600	7BCLS-2R	70–2R	30
34–46	5500–6600	7BCLS-3R	100–3R	30
46–56	5500–6600	7BCLS-4R	130–4R	30
56–68	5500–6600	7BCLS-5R	150–5R	30
68–85	5500–6600	7BCLS-6R	170–6R	30
85–137	5500–6600	7BCLS-9R	200–9R	30
137–187 ①	5500–6600	7BCLS-12R	230–12R	30
273–400 ②	5500–6600	7BCLS-24R	450–24R	250

Notes

① For FLA >180, maximum acceleration time = 4.5 seconds.

② For FLA >360, maximum acceleration time = 6 seconds.

Fuse selections based on LRC = FLA x 6 with acceleration time of 10 seconds except where otherwise noted.

SL Series Ratings

Type SL Vacuum Contactor Ratings (7.2 kV/160–400A)

	Interrupting Rating		Application Table					
				Synchronous Motor Horsepower				
Rated Utilization Voltage	NEMA Unfused (E1) kA	NEMA Fused (E2) kA	Induction Motor Horsepower	(0.8 PF)	(1.0 PF)	Transformer kVA	Capacitor kVAR	Maximum Insulation Voltage
7.2 kV/160A Frame								
2200–2500	4.5	50	600	600	800	600	480	7200
3000–3600	4.5	50	900	900	1000	800	640	7200
3800–4800	4.5	50	1200	1200	1400	1000	960	7200
6000–6900	4.5	50	1800	1800	2200	1600	1320	7200
7.2 kV/200A Frame								
2200–2500	4.5	50	800	800	1000	750	600	7200
3000–3600	4.5	50	1100	1100	1250	1000	800	7200
3800–4800	4.5	50	1500	1500	1750	1250	1200	7200
6000–6900	4.5	50	2250	2250	2750	2000	1650	7200
7.2 kV/360A Frame								
2200–2500	4.5	50	1500	1500	1750	1200	1000	7200
3000–3600	4.5	50	2000	2000	2500	1600	1475	7200
3800–4800	4.5	50	2500	2500	3000	2000	2150	7200
6000–6900	4.5	50	4000	4000	5000	3200	2950	7200
7.2 kV/400A Frame								
2200–2500	8.5	50	1750	1750	2000	1500	1200	7200
3000–3600	8.5	50	2250	2250	2500	2000	1650	7200
3800–4800	8.5	50	3000	3000	3500	2500	2400	7200
6000–6900	8.5	50	4500	4500	5500	4000	3300	7200

Rating Specifications (7.2 kV/160–400A)

Ampere Rating	7.2 kV/160A	7.2 kV/200A	7.2 kV/60A	7.2 kV/400A
Maximum Interrupting Current (Three operations—amperes)	4500	4500	4500	8500
Rated Current	160	200	360	400
IEC Make-Break Capability—AC4 (Amperes) Make	1600	2000	3600	4000
Break	1280	1600	2880	3200

Product Specifications

7.2 kV/160–400A

- Short-time current:
  - 30 seconds: 2400A
  - 1 second: 6000A
  - 8.7 ms: 63 kA peak (0.5 cycle)
- Normal service altitude: –3281 to +6562 ft (–1000 to +2000m)
- Mechanical life: 2.5 million
- Electrical life:
  - 6 x Rated Make/1x Rated Break: 300,000 operations
  - 6 x Rated Make/6 x Rated Break: 300,000 operations
- BIL (impulse withstand): 60 kV (1.2 x 50 microseconds)
- Dielectric strength: 20 kV rms (1 minute)
- Closing time: 80 ms (energization to contact touch)
- Selectable opening times:
  - 30 ms (2 cycles)
  - 50 ms (3 cycles)
  - 130 ms (8 cycles)
  - 250 ms (15 cycles)
  - 330 ms (20 cycles)
- Arcing time: 12 ms (0.75 cycle) or less
- Pickup voltage: 80% rated coil voltage
- Dropout voltage: 60% rated coil voltage
- Control voltages:
  - AC/Hz: 110/50, 120/60, 220/50, 240/60
  - DC: 125
- Control circuit burden:
  - Closing: (200 ms)
    - 110/120 AC, 125 DC 1 kVA
    - 220/240 AC 1.8 kVA
  - Holding:
    - 110/120 AC, 125 DC 40 VA
    - 220/240 AC 50 VA
- Auxiliary contact rating:
  - 600V (maximum)
  - 10A continuous current
  - Making capacity
    - AC: 7200 VA
    - DC: 125 VA
  - Breaking capacity
    - AC: 720 VA
    - DC: 125 VA
- Latch (when specified)
  - Mechanical life: 250,000 operations
  - Trip voltage
    - DC: 24V
    - DC: 125V
    - AC: 110/120V
  - Minimum trip voltage: 80% rated coil voltage
  - Trip burden
    - 24 Vdc: 400 VA
    - 48 and 125 Vdc: 400 VA
    - 110 and 120 Vac: 400 VA
    - 220 and 240 Vac: 400 VA
  - Trip time (2 cycles): 30 ms
- Weight
  - 150–360A: 47 lbs (21.3 kg)
  - 400A: 49 lbs (22.2 kg)

Wiring Diagrams

Electrical Connections Diagrams (7.2 kV/160–400A)

Connection for Magnetically Held Contactor



Connections for Mechanically Latched Contactor



Note

① M contacts are connected in parallel for AC voltages and for ≤48 Vdc.
M contacts are connected in series for >48 Vdc.

Dimensions

Approximate Dimensions in Inches (mm)

Dimensional Drawings 7.2 kV/160–400A

Front



Rear



Base Plate



Side



Approximate Dimensions in Inches (mm)

Lug Terminal



Lug Terminal



Upper Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
7.2 kV/160	0.75 (19.1)	1.31 (33.3)	10
7.2 kV/200	1.00 (25.4)	1.31 (33.3)	10
7.2 kV/360	1.00 (25.4)	1.31 (33.3)	10
7.2 kV/400	1.00 (25.4)	1.31 (33.3)	10

Lower Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
7.2 kV/160	1.25 (31.8)	1.10 (27.9)	10
7.2 kV/200	1.25 (31.8)	1.10 (27.9)	10
7.2 kV/360	1.25 (31.8)	1.10 (27.9)	10
7.2 kV/400	1.25 (31.8)	1.10 (27.9)	10

SL 7.2 kV/800A Medium Voltage Contactor



Contents

Description	*Page*
Product Overview	**V4-T3-72**
SL MV Power Contactor 7.2 kV/160–400A	**V4-T3-74**
SL MV Power Contactor 7.2 kV/800A	
Options and Accessories	**V4-T3-84**
Technical Data and Specifications	**V4-T3-84**
Dimensions	**V4-T3-86**
SL MV Power Contactor 15 kV/300A	**V4-T3-87**

SL MV Power Contactor 7.2 kV/800A

Product Description

- A single family of contactors for any medium voltage control application. Voltage range of 2200–7200V
- 800A rating with induction motor horsepower ranges from 3000 to 10,000 hp

Application Description

Eaton's SL Medium Voltage Contactors starting applications:

- Squirrel-cage induction motors
- Synchronous motors
- Wound-rotor

Fully applicable to:

- Full voltage starting
- Reduced voltage starting

The perfect choice for harsh duty applications:

- Mining
- Pulp and paper
- HVAC
- Petrochemical
- Automotive
- Many others

Features, Benefits and Functions

- Two different altitude versions
- Leading-edge vacuum technology
- Long life—200,000 electrical and 250,000 mechanical
- Special ordering allows unit to be factory pre-set to customer specification, including field kit installation
- Highest quality available—all contactors manufactured within state-of-the-art "ISO-Certified" facilities. 100% made in America

Factory Installed Option Kit

- Mechanical latch—many coil voltages

Standards and Certifications

Acceptability

- NEMA
- ANSI
- IEC

Third-Party Verification

- UL
- CSA
- KEMA

Design and Test Standards

- UL 347, File No. E63257
- CSA
- ANSI/NEMA ICS 3
- IEC 60470

Product Selection

Contact Eaton for pricing.

Options and Accessories

SL Series—Accessory Options 800A



Mechanical Latch Assembly 800A

Mechanical Latch Option—SL Vacuum Contactor Size 800A
Factory installed for 800A SL Vacuum Contactor. Coil voltages available in a wide range of AC and DC selections.

Technical Data and Specifications

The SL Contactor Ratings
- Voltages of 2200–7200V
- 800A (720A enclosed)
- Interrupting rating of 12,500A

Control Voltages
- 110, 220 Vac, 50 Hz
- 120, 240 Vac, 60 Hz
- 125 Vdc

Dropout Time
- 50–330 ms, field selectable

Front and Rear View 7.2 kV/800A



Front View



Rear View

SL Series Fuses

Fuse Application Table for SL Contactors 7.2 kV/SL-800

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
225–360	2400–4800	5BCLS-24R	450–24R	50
360–449	2400–4800	5BCLS-36R	650–36R	130
450–720	2400–4800	5BCLS-44R	800–44R	250
225–400	5500–6600	7BCLS-24R	450–24R	50
400–449	5500–6600	7BCLS-36R	650–36R	130
450–720	5500–6600	7BCLS-44R	800–44R	250

Note
Fuse selections based on LRC = FLA x 6 with acceleration time of 10 seconds.

SL Series Ratings

Type SL Vacuum Contactor Ratings 7.2 kV/SL-800

	Interrupting Rating		Application Table					
				Synchronous Motor Horsepower				
Rated Utilization Voltage	NEMA Unfused (E1) kA	NEMA Fused (E2) kA	Induction Motor Horsepower	(0.8 PF)	(1.0 PF)	Transformer kVA	Capacitor kVAR	Maximum Insulation Voltage
2200–2500	12.5 (50 MVA)	50 (200 MVA at 2300V)	3000	3000	3500	2500	2400	7200
3000–3600	12.5 (50 MVA)	50 (285 MVA at 3300V)	4000	4000	5000	3500	3200	7200
3800–5000	12.5 (75 MVA)	50 (400 MVA at 4600V)	5000	5000	6000	4500	4000	7200
6000–7200	12.5 (100 MVA)	50 (570 MVA at 6600V)	8000	8000	10,000	6000	4800	7200

Rating Specifications 7.2 kV/SL-800

Ampere Rating	7.2 kV/800A
Maximum Interrupting Current (Three operations—amperes)	12,500
Rated Current	800 (720 enclosed)
IEC Make-Break Capability—AC4 (Amperes)	
Make	7650
Break	6120

Product Specifications

7.2 kV/800A

- Short-time current
  - 30 seconds: 4320A
  - 1 second: 10,800A
  - 8.7 ms (0.5 cycle) 86 kA peak
- Normal service altitude: –3281 to +6562 ft (–1000 to +2000m)
- Mechanical life: 250,000
- Electrical life: 200,000 operations
- BIL (impulse withstand): 60 kV (1.2 x 50 microseconds)
- Dielectric strength: 18.2 kV rms (1 minute)
- Closing time (energization to contact touch): 80 ms
- Opening times (de-energization to full open):
  - 50 ms (3 cycles)
  - 130 ms (8 cycles)
  - 200 ms (12 cycles)
  - 330 ms (20 cycles)
- Arcing time: 12 ms (0.75 cycle) or less
- Pickup voltage: 80% rated coil voltage
- Dropout voltage: 60% rated coil voltage
- Control voltages:
  - AC/Hz: 110/50, 120/60 Vac, 220/50, 240/60
  - DC: 125 Vdc
- Control circuit burden:
  - Closing (120/240): 2600 VA
  - Holding (120/240): 50 VA
- Auxiliary contact rating:
  - 600V (maximum)
  - 10A continuous current
  - Making capacity
    - AC: 7200 VA
    - DC: 200 VA
  - Breaking capacity
    - AC: 720 VA
    - DC: 200 VA
- Latch (when specified):
  - Mechanical life: 250,000 operations
  - Trip voltage
    - DC: 24, 48, 96V
    - AC: 110/120, 220/240V 50/60 Hz
  - Minimum trip voltage: 80% rated coil voltage
  - Trip burden
    - 24 Vdc: 1200 VA
    - 48 and 96 Vdc: 400 VA
    - 110 and 220 Vac: 500 VA
  - Trip time (2 cycles): 30 ms
- Weight: 95 lbs (43.1 kg)

Dimensions

Approximate Dimensions in Inches (mm)

Dimensional Drawings 7.2 kV/800A

3

Side



Top



Front



Lug Terminal



Detail A
Line Lug Terminal
Use 10 mm or 3/8 inch Bolt



Detail B
Load Lug Terminal
Use 10 mm or 3/8 inch Bolt

Lug Terminal



Upper Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
7.2 kV/800	1.75 (44.5)	2.00 (50.8)	10

Lower Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
7.2 kV/800	1.50 (38.1)	1.50 (38.1)	10

SL 15 kV/300A Medium Voltage Contactor



Contents

Description	*Page*
Product Overview	**V4-T3-72**
SL MV Power Contactor 7.2 kV/160–400A	**V4-T3-74**
SL MV Power Contactor 7.2 kV/800A	**V4-T3-83**
SL MV Power Contactor 15 kV/300A	
Options and Accessories	**V4-T3-88**
Technical Data and Specifications	**V4-T3-88**
Dimensions	**V4-T3-90**

SL MV Power Contactor 15 kV/300A

Product Description

- A single family of contactors for any medium voltage control application. Voltage range of 7200–15,000V
- 300A rating with induction motor horsepower ranges from 500 to 7500 hp
- Two different altitude versions
- Leading-edge vacuum technology
- Long life—200,000 electrical and 250,000 mechanical operations
- Special ordering allows unit to be factory pre-set to customer specification, including field kit installation
- Highest quality available—all contactors manufactured within state-of-the-art "ISO-Certified" facilities. 100% made in America

Application Description

Eaton's SL Medium Voltage Contactors starting applications:

- Squirrel-cage induction motors
- Synchronous motors
- Wound-rotor

Fully applicable to:

- Full voltage starting
- Reduced voltage starting

The perfect choice for harsh duty applications:

- Mining
- Pulp and paper
- HVAC
- Petrochemical
- Automotive
- Many others

Features, Benefits and Functions

Factory Installed Option Kit

- Mechanical latch—many coil voltages

Standards and Certifications

Acceptability

- NEMA
- ANSI
- IEC

Third-Party Verification

- UL
- CSA
- KEMA

Design and Test Standards

- UL 347, File No. E63257
- CSA
- ANSI/NEMA ICS 3
- IEC 60470

Product Selection

Contact Eaton for pricing.

Options and Accessories

SL Series—Accessory Options 15 kV/300A



Mechanical Latch Assembly 15 kV/300A

Mechanical Latch Option—SL Vacuum Contactor
Factory installed for 15 kV/300A SL Vacuum Contactor. Coil voltages available in a wide range of AC and DC selections.

Technical Data and Specifications

The SL Contactor Ratings
- Voltages to 15,000V
- 300A
- Interrupting rating of 5000A

Control Voltages
- 110, 220 Vac, 50 Hz
- 120, 240 Vac, 60 Hz
- 125 Vdc

Dropout Time
- 50–330 ms
- Field selectable

Front and Rear View 15 kV/300A



Front View

Rear View

SL Series Fuses

Fuse Application Table for SL Contactors 15 kV/SL-300A

Motor FLA	Voltage	Suggested Eaton Fuse	Rating	Minimum Opening Time
50–300 ①	10,000–13,800	15BHCLS-400	400	130 ms

Notes

① For FLA >275, contact factory for maximum acceleration time.

Fuse selections based on LRC = FLA x 6 with acceleration time of 10 seconds except where otherwise noted.

SL Series Ratings

Type SL Vacuum Contactor Ratings 15 kV/300A

	Interrupting Rating		Application Table					
				Synchronous Motor Horsepower				
Rated Utilization Voltage	NEMA Unfused (E1) kA	NEMA Fused (E2) kA	Induction Motor Horsepower	(0.8 PF)	(1.0 PF)	Transformer kVA	Capacitor kVAR	Maximum Insulation Voltage
10,000–11,000	5	50 (950 MVA at 11,000V)	6000	6000	6750	5500	Consult factory	15,000
12,400–13,800	5	50 (1190 MVA at 13,800V)	7500	7500	8500	6800	Consult factory	15,000

Rating Specifications 15 kV/300A

Ampere Rating	15 kV/300A
Maximum Interrupting Current (Three operations—amperes)	5000
Rated Current	300
IEC Make-Break Capability—AC4 (Amperes) Make	3000
Break	3000

Product Specifications

15 kV/300A

- Short-time current
  - 30 seconds: 1800A
  - 1 second: 4500A
  - 8.7 ms (0.5 cycle) 25 kA peak
- Normal service altitude: –3281 to +6562 ft (–1000 to +2000m)
- Mechanical life: 250,000 operations
- Electrical life: 200,000 operations
- BIL (impulse withstand): 75 kV (1.2 x 50 microseconds)
- Dielectric strength: 36 kV rms (1 minute)
- Closing time (energization to contact touch): 80 ms
- Selectable opening times (de-energization to full open):
  - 50 ms (3 cycles)
  - 130 ms (8 cycles)
  - 250 ms (12 cycles)
  - 330 ms (20 cycles)
- Arcing time: 12 ms (0.75 cycle) or less
- Pickup voltage: 80% rated coil voltage
- Dropout voltage: 60% rated coil voltage
- Control voltages:
  - AC/Hz: 110/50, 120/60 Vac, 220/50, 240/60
  - DC: 125 Vdc
- Control circuit burden:
  - Closing (120/240): 1700/2600 VA
  - Holding (120/240): 80 VA
- Auxiliary contact rating:
  - 600V (maximum)
  - 10A continuous current
  - Making capacity
    - AC: 7200 VA
    - DC: 200 VA
  - Breaking capacity
    - AC: 720 VA
    - DC: 200 VA
- Latch (when specified):
  - Mechanical life: 250,000 operations
  - Trip voltage
    - DC: 24, 48, 96V
    - AC: 110/120, 220/240V, 50/60 Hz
  - Minimum trip voltage: 80% rated coil voltage
  - Trip burden
    - 24 Vdc: 1200 VA
    - 48 and 96 Vdc: 400 VA
    - 110 and 220 Vac: 500 VA
  - Trip time (2 cycles): 30 ms
- Weight: 95 lbs (43.1 kg)

Dimensions

Approximate Dimensions in Inches (mm)

Dimensional Drawings 15 kV/300A

3

Front



Front View

Side 15 kV/300A



RH Side View

Top



Top View

Lug Terminal



Lug Terminal



Upper Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
15 kV/300	1.25 (31.8)	1.25 (31.8)	10

Lower Lug Terminal

Contactor Ampere Rating	Width	Depth	Hardware (Bolt Diameter)
15 kV/300	1.50 (38.1)	1.25 (38.1)	10

Contents

Description

Fuses General

Product Overview

Power Fuse

Eaton's roots in the medium voltage power fuse business began over 75 years ago under Westinghouse® Electric. In 1935, Westinghouse introduced the medium voltage boric acid expulsion fuse followed by the medium voltage current limiting fuse. Even today, medium voltage fuses continue to use that core technology. Eaton continues to build on the technology legacy by engineering higher performance, cost-effective power fuse products.

Eaton's medium voltage fuses are manufactured and tested to the requirements of the C37-4X series of standards, which are maintained and updated regularly to maintain currency with industry practices. These standards are:

IEEE Std. C37.40™

IEEE Standard Service Conditions and Definitions for High Voltage Fuses, Distribution Enclosed Single-Pole Air Switches, Fuse Disconnecting Switches, and Accessories (ANSI).

IEEE Std. C37.41™

IEEE Standard Design Tests for High-Voltage (>1000V) Fuses, Fuse and Disconnecting Cutouts, Distribution Enclosed Single-Pole Air Switches, Fuse Disconnecting Switches, and Fuse Links and Accessories used with These Devices (ANSI).

ANSI C37.42™

IEEE Standard Specifications for High-Voltage (>1000V) Expulsion-Type Distribution-Class Fuses, Fuse and Disconnecting Cutouts, Fuse Disconnecting Switches, and Fuse Links, and Accessories used with These Devices (ANSI).

ANSI C37.46

American National Standard for High Voltage Expulsion and Current Limiting Type Power Class Fuses and Fuse Disconnecting Switches.

ANSI C37.47

American National Standard for High Voltage Current Limiting Type Distribution Class Fuses and Fuse Disconnecting Switches.

The following IEEE standards are also applicable to the fuse products covered in this publication:

IEEE Std. C37.48™

IEEE Guide for the Application, Operation, and Maintenance of High Voltage Fuses, Distribution Enclosed Single-Pole Air Switches, Fuse Disconnecting Switches, and Accessories (ANSI).

IEEE Std. C37.48.1™

IEEE Guide for the Classification, Application, and Coordination of Current-Limiting Fuses with Rated Voltages 1–38 kV.

A better understanding of some fuse terminology will help you understand and select the correct fuse. The following is a brief overview of those terms.

Power vs. Distribution

The differentiation is intended to indicate the test conditions and where fuses are normally applied on an electrical system, based on specific requirements for generating sources, substations and distribution lines. Each class has its own unique set of voltage, current and construction requirements (see C37.42, .46 and .47).

Low vs. Medium vs. High Voltage

While fuses are defined in the ANSI standards as either low or high voltage, Eaton has elected to name their fuses to correspond with the equipment in which they are installed. Therefore, per ANSI C84, our fuses are named as follows:

- Low voltage—1000V and below
- Medium voltage—greater than 1000 to 69,000V
- High voltage—greater than 69,000V

Expulsion vs. Current Limiting (Definitions per ANSI C47.40-1993)

An expulsion fuse is a vented fuse in which the expulsion effect of the gases produced by internal arcing, either alone or aided by other mechanisms, results in current interruption.

An expulsion fuse is not current limiting and as a result limits the duration of a fault on the electrical system, not the magnitude.

A current limiting fuse is a fuse that, when its current responsive element is melted by a current within the fuse's specified current limiting range, abruptly introduces a high resistance to reduce current magnitude and duration, resulting in subsequent current interruption. Refer to Fuse Types Protection Range figure on **Page V4-T3-93** for a features comparison.

Fuse Types

There are three current limiting fuse types: Backup, General Purpose and Full Range. It is important that the user have an understanding of these definitions to ensure proper application of the fuse (see Fuse Types Protection Range figure on **Page V4-T3-93**).

Backup Fuses

A fuse capable of interrupting all currents from the maximum rated interrupting current down to the rated minimum interrupting current.

Backup fuses are always used in a series with another interrupting device capable of interrupting currents below the fuse's minimum interrupting current.

General Purpose Fuses

A fuse capable of interrupting all currents from the rated interrupting current down to the current that causes melting of the fusible element in no less than one hour.

General Purpose fuses are typically used to protect feeders and components such as transformers.

Full Range Fuses

A fuse capable of interrupting all currents from the rated interrupting current down to the minimum continuous current that causes melting of the fusible element, with the fuse applied at the maximum ambient temperature specified by the manufacturer.

General Fuse Component Terms

Fuse Refill Unit (of an Expulsion Fuse)

A fuse refill unit is a replaceable assembly containing the calibrated current-responsive fuse element and certain other items that facilitate current interruption. On its own, the refill unit has no interrupting ability. A refill unit must be mounted in a fuseholder with a spring assembly to form a refillable fuse unit. The refill unit is the section of the fuse that must be replaced after a fuse operation.

Fuseholder (of an Expulsion Fuse)

A fuseholder is a reusable holder that when equipped with a fuse refill unit forms a fuse unit, capable of interrupting an overload or fault current. A fuseholder is supplied with a spring and shunt assembly, necessary to complete the internal interrupting assembly. The spring and shunt assembly is supplied with the fuseholder but is also available as a replacement part, as it may need replacement after several of heavy operations.

Fuse Unit

A fuse unit is a replaceable unit or assembly that is able, on its own, to perform current interruption. In the case of a refillable fuse unit, the refill unit must be replaced after a fuse operation. Where a complete fuse unit is supplied from the factory, the complete fuse unit must be replaced after a fuse operation. All current-limiting fuses are fuse units.

Exhaust Control Device

When expulsion fuses are used in enclosures, exhaust control devices (filters, condensers or mufflers) are used to control the sound of the fuse operation, and to de-ionize and absorb the fuse exhaust products. These devices are normally supplied separately, because of different characteristics and ratings. They are reusable but may need replacement after several heavy operations.

Mounting

A mounting provides all the necessary parts to safely mount a fuse in its intended piece of equipment. The base is the metal support to which all other pieces attach. Insulators attach to the base and insulate the live fuse unit from the base and everything beyond the base. Live parts are the parts of the mounting that are energized once electricity is flowing. The live parts provide the means to hold the fuse unit in place, electrical contact, and a place to make line and load connections.

Non-Disconnect Mounting

A non-disconnect mounting does not provide a means for removing the fuse unit until the circuit is dead and the fuse unit can be removed manually. The fuse unit is held in place by friction through the use of fuse clips or by a cross bar.

Disconnect Mounting

The disconnect mounting allows the fuse unit to be removed (off load) using an insulated hook stick. The hookstick grabs a pull ring and disconnects the fuse unit, which may then be lifted out of its mounting.

Dropout Mounting

Dropout mountings are used in outdoor applications. The fuse unit is equipped with a mechanical trigger that unlatches the upper contact, allowing the fuse unit to drop out, increasing the dielectric separation, and providing visible indication of a blown fuse.

Live Parts

Live parts were briefly discussed as part of the "Mounting" definition. Everything above the insulators on the mounting excluding the fuse unit, fuse holder, and the fuse end fittings (if required) are considered the live parts. Fuse end fittings are discussed next and are not required with non-disconnect live parts, but are required and included with disconnect live parts. Live parts may be sold separately as replacement parts or for new OEM applications.

End Fittings

End fittings are metal parts that attach to each end of a fuse unit's ferrules (end caps). As previously mentioned, they are used solely with disconnect fuse applications or when converting a non-disconnect to a disconnect fuse configuration.

When end fittings are ordered, a fitting for each end of the fuse is included. Keep in mind that end fittings can become damaged in use and, therefore, are sold separately from the live parts when necessary. It is not necessary to purchase an entire set of live parts when only the end fittings are required.

General High Voltage Fuse Comparison

Expulsion	Current Limiting
Vented	Sealed
Electromechanical	Static
Interrupts at current zero	Limits fault current
Generally higher voltage and current application capabilities	Generally higher interrupting ratings
Different time/current characteristics	Different time/current characteristics

Fuse Types Protection Range



Contents

Description	*Page*
Catalog Number Selection	**V4-T3-95**
Product Selection	**V4-T3-96**

Product Description

Eaton's expulsion fuses use boric acid as the interrupting medium. Under a fault condition, arc heat decomposes the boric acid into water vapor. The water vapor blast deionizes the arc path preventing arc re-ignition after a natural current zero.

Type RBA indoor expulsion fuses must be fitted with a discharge filter or condenser, that moderates the discharge exhaust. The discharge filter limits the exhaust to a small and relatively inert amount of gas and lowers the noise level without affecting the fuse interrupting rating. Steam discharge, that can effect the interrupting, is fully restricted by the condenser.

Type RDB outdoor dropout fuses include an ejector spring that forces the arcing rod through the top of the fuse. The arcing rod strikes a latch on the mounting that forces the fuse to swing outward through a 180° arc into the dropout position.

Refill units can be field installed into RBA and RDB expulsion fuses. Once the operated unit has been removed, the separately purchased unit can be easily installed into the fuse holder.

Type DBU fuse units are designed for new and aftermarket utility applications. End fittings are available, in both indoor and outdoor versions, as well as live parts and mountings. Mufflers confine the arc within the fuse and substantially reduce the noise and exhaust when the fuse interrupts.

RBA E-Rated Refillable Boric Acid

RDB E-Rated Refillable Outdoor Dropout Boric Acid

DBU Dropout Boric Acid—for Use Indoors, Inside Switchgear or Outdoors

Accessories

The following accessories are available for expulsion fuses:

Mountings

Mountings include a base, porcelain or glass polyester insulators, and live parts. They help enable the fuse to be safely attached to the gear. Mountings can be either disconnect, nondisconnect or dropout. Non-disconnect mountings are available in bolt-on or clamp-type arrangements. Fuses may be vertical or underhung.

Live Parts

Live parts attach the fuse to the insulators and are considered part of the mounting. All parts above the insulators are live parts.

End Fittings

End fittings are metal parts that attach to each end of the fuse at the ferrules. They are used only on disconnect fuses or when converting a nondisconnect to a disconnect fuse.

Catalog Number Selection

Expulsion Fuse

Easy to Use, Easy to Order!
Eaton's fuse catalog numbering system makes it easy to order the right fuse. The catalog numbers are easy to remember, unique to each fuse, and are broken down in three descriptive segments: Fuse Type, Voltage Rating and Current Rating.

These Catalog numbers can be entered directly and easily:

- No change in order processing will occur if you use either a style number or its corresponding catalog number. You will get the same fuse
- If you are ordering a replacement for an older Westinghouse fuse, it will only have the style number. Order under this style number and you will get the correct fuse

Examples:

8RBA2-10E	8.3 max. kV, RBA-200 refill, 10E amperes
DBU17-30K	17.1 max. kV, DBU fuse unit, 30 amperes
15RBA8-INH	15.5 max. kV, RBA-800, indicating nondisconnect holder
RBA4-FLTR	RBA-400 filter

Expulsion Fuse Units

15 DBU 17 - 100 E

Maximum kV	Type	Maximum kV	Amperes		Speed
8	RBA	17	0.5	50	E
15	DBU	27	3	65	K
25	DBA	38	5	80	SE
38	RDB		7	100	
48	RBT		10	125	
72	BA		15	150	
92			20	200	
121			25	250	
145			30	300	
			40	400	

Expulsion Fuse Accessories

15 RBA2 - P NM

Maximum kV	Type	Insulator	Hardware	
8	RBA	G = Glass polyester	UM	= Underhung mounting
15	DBU	P = Porcelain	VM	= Vertical mounting
17	RDB	H = High BIL	DL	= Disconnect live parts
25	BA		NL	= Nondisconnect live parts
27			DH	= Disconnect holder
38			NH	= Nondisconnect holder
			NM	= Nondisconnect mounting
			UL	= Underhung live parts
			VL	= Vertical live parts
			I	= Indicating
			O	= Outdoor
			FLTR	= Filter
			COND	= Condenser
			MFLR	= Muffler
			SHNT	= Shunt and spring assembly

Product Selection

Contact Eaton for pricing.

Type RBA and RDB

3

Type 8RBA2 Expulsion Fuse Refill Units—8.3 kV Maximum (7.2 kV Nominal) 200A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
10E	**8RBA2-10E**	1, 2	—	—	1.0 (0.45)
15E	**8RBA2-15E**	1, 2	—	—	1.0 (0.45)
20E	**8RBA2-20E**	1, 2	**8RBT2-20E**	3, 4	1.0 (0.45)
25E	**8RBA2-25E**	1, 2	**8RBT2-25E**	3, 4	1.0 (0.45)
30E	**8RBA2-30E**	1, 2	**8RBT2-30E**	3, 4	1.0 (0.45)
40E	**8RBA2-40E**	1, 2	**8RBT2-40E**	3, 4	1.0 (0.45)
50E	**8RBA2-50E**	1, 2	**8RBT2-50E**	3, 4	1.0 (0.45)
65E	**8RBA2-65E**	1, 2	**8RBT2-65E**	3, 4	1.0 (0.45)
80E	**8RBA2-80E**	1, 2	**8RBT2-80E**	3, 4	1.0 (0.45)
100E	**8RBA2-100E**	1, 2	**8RBT2-100E**	3, 4	1.0 (0.45)
125E	**8RBA2-125E**	1, 2	**8RBT2-125E**	3, 4	1.0 (0.45)
150E	**8RBA2-150E**	1, 2	**8RBT2-150E**	3, 4	1.0 (0.45)
200E	**8RBA2-200E**	1, 2	**8RBT2-200E**	3, 4	1.0 (0.45)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—8.3 kV Maximum (7.2 kV Nominal) 200A (For Use with 8RBA2 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Non-disconnect	**8RBA2-NH**	**8RBA2-INH**	4.8	5.5	60	**5RBA2-PNM**	**5RBA2-GNM**	**15RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**
	Non-disconnect	**8RBA2-NH**	**8RBA2-INH**	7.2	8.3	75	**8RBA2-PNM**	**8RBA2-GNM**	**15RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**
	Disconnect	**8RBA2-DH**	**BRBA2-IDH**	4.8	5.5	60	**5RBA2-PDM**	**5RBA2-GDM**	**14RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**
	Disconnect	**8RBA2-DH**	**BRBA2-IDH**	7.2	8.3	75	**8RBA2-PDM**	**8RBA2-GDM**	**14RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**
	Bolt-in	—	**8RBA2-INH-B**	4.8	5.5	60	**5RBA8-PNM**	**5RBA8-GNM**	**15RBA8-NL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**
	Bolt-in	—	**8RBA2-INH-B**	7.2	8.3	75	**8RBA8-PNM**	**8RBA8-GNM**	**15RBA8-NL**	**RBA2-FLTR** **RBA2-COND**	**8RBA2-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—8.3 kV Maximum (7.2 kV Nominal) 200A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Dropout	**8RDB2-DH**	7.2	8.3	95	**8RDB2-VM**	**8RDB2-UM**	**RDB2-VL**	**RDB2-UL**	**8RDB2-SHNT**
	Dropout	**8RDB2-DH**	7.2	8.3	110	**8RDB2-HVM**	**8RDB2-HUM**	**RDB2-VL**	**RDB2-UL**	**8RDB2-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the |user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 8RBA4 Expulsion Fuse Refill Units—8.3 kV Maximum (7.2 kV Nominal) 400A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
0.5	**8RBA4-.5**	5, 6	—	—	2.1 (0.95)
3	**8RBA4-3**	5, 6	—	—	2.1 (0.95)
5E	**8RBA4-5E**	5, 6	—	—	2.1 (0.95)
7E	**8RBA4-7E**	5, 6	—	—	2.1 (0.95)
10E	**8RBA4-10E**	5,6	—	—	2.1 (0.95)
15E	**8RBA4-15E**	5, 6	—	—	2.1 (0.95)
20E	**8RBA4-20E**	5, 6	**8RBT4-20E**	7, 8	2.1 (0.95)
25E	**8RBA4-25E**	5, 6	**8RBT4-25E**	7, 8	2.1 (0.95)
30E	**8RBA4-30E**	5, 6	**8RBT4-30E**	7, 8	2.1 (0.95)
40E	**8RBA4-40E**	5, 6	**8RBT4-40E**	7, 8	2.1 (0.95)
50E	**8RBA4-50E**	5, 6	**8RBT4-50E**	7, 8	2.1 (0.95)
65E	**8RBA4-65E**	5, 6	**8RBT4-65E**	7, 8	2.1 (0.95)
80E	**8RBA4-80E**	5, 6	**8RBT4-80E**	7, 8	2.1 (0.95)
100E	**8RBA4-100E**	5, 6	**8RBT4-100E**	7, 8	2.1 (0.95)
125E	**8RBA4-125E**	5, 6	**8RBT4-125E**	7, 8	2.1 (0.95)
150E	**8RBA4-150E**	5, 6	**8RBT4-150E**	7, 8	2.1 (0.95)
200E	**8RBA4-200E**	5, 6	**8RBT4-200E**	7, 8	2.1 (0.95)
250E	**8RBA4-250E**	5, 6	**8RBT4-250E**	10, 11	2.1 (0.95)
300E	**8RBA4-300E**	5, 6	**8RBT4-300E**	10, 11	2.1 (0.95)
400E	**8RBA4-400E**	5, 6	**8RBT4-400E**	10, 11	2.1 (0.95)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—8.3 kV Maximum (7.2 kV Nominal) 400A (For Use with 8RBA4 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–400E	Non-disconnect	**8RBA4-NH**	**8RBA4-INH**	4.8	5.5	60	**5RBA4-PNM**	**5RBA4-GNM**	**15RBA4-NL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**
	Non-disconnect	**8RBA4-NH**	**8RBA4-INH**	7.2	8.3	75	**8RBA4-PNM**	**8RBA4-GNM**	**15RBA4-NL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**
	Disconnect	**8RBA4-DH**	**BRBA2-IDH**	4.8	5.5	60	**5RBA4-PDM**	**5RBA4-GDM**	**14RBA4-DL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**
	Disconnect	**8RBA4-DH**	**BRBA2-IDH**	7.2	8.3	75	**8RBA4-PDM**	**8RBA4-GDM**	**14RBA4-DL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**
	Bolt-in	—	**8RBA2-INH-B**	4.8	5.5	60	**5RBA8-PNM**	**5RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**
	Bolt-in	—	**8RBA4-INH-B**	7.2	8.3	75	**8RBA8-PNM**	**8RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** **RBA4-COND**	**8RBA4-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—8.3 kV Maximum (7.2 kV Nominal) 400A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–400E	Dropout	**8RDB4-DH**	7.2	8.3	95	**8RDB4-VM**	**8RDB4-UM**	**RDB4-VL**	**RDB4-UL**	**8RDB4-SHNT**
	Dropout	**8RDB4-DH**	7.2	8.3	110	**8RDB4-HVM**	**8RDB4-HUM**	**RDB4-VL**	**RDB4-UL**	**8RDB4-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 8RBA4 Expulsion Fuse Refill Units Used in 8RBA8/8RDB4 Fuseholders—8.3 kV Maximum (7.2 kV Nominal) 800A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
450E	2	**8RBA4-250E**	9	2	**8RBT4-250E**	12	①
540E	2	**8RBA4-300E**	9	2	**8RBT4-300E**	12	①
720E	2	**8RBA4-400E**	9	2	**8RBT4-400E**	12	①

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—8.3 kV Maximum (7.2 kV Nominal) 800A (For Use with 8RBA8 Fuseholders) ②

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
450E–720E	Non-disconnect	**8RBA8-NH**	**8RBA8-INH**	4.8	5.5	60	**5RBA8-PNM**	**5RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**8RBA4-SHNT**
	Non-disconnect	**8RBA8-NH**	**8RBA8-INH**	7.2	8.3	75	**8RBA8-PNM**	**8RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**8RBA4-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—8.3 kV Maximum (7.2 kV Nominal) 800A ④

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
450E–720E	Disconnect	**8RDB4-NH**	7.2	8.3	95	**8RDB8-VM**	**8RDB8-UM**	**RDB8-VL**	**RDB8-UL**	**8RDB4-SHNT**
	Disconnect	**8RDB4-NH**	7.2	8.3	110	**8RDB8-HVM**	**8RDB8-HUM**	**RDB8-VL**	**RDB8-UL**	**8RDB4-SHNT**

Notes

① Requires two fuse refills as shown. Price each refill individually. Example: To order refill units for a 720E, 8.3 kV fuse, order two pieces of an 8RBA4-400E.

② For new installation, order two refills (Standard or Time Lag), one fuseholder, one mounting, and two filters or condensers per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

③ Two filters or condensers required.

④ For new installation, order two refills (Standard or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 15RBA2 Expulsion Fuse Refill Units—15.5 kV Maximum (14.4 kV Nominal) 200A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
10E	**15RBA2-10E**	1, 2	—	—	1.1 (0.5)
15E	**15RBA2-15E**	1, 2	—	—	1.1 (0.5)
20E	**15RBA2-20E**	1, 2	**15RBT2-20E**	3, 4	1.1 (0.5)
25E	**15RBA2-25E**	1, 2	**15RBT2-25E**	3, 4	1.1 (0.5)
30E	**15RBA2-30E**	1, 2	**15RBT2-30E**	3, 4	1.1 (0.5)
40E	**15RBA2-40E**	1, 2	**15RBT2-40E**	3, 4	1.1 (0.5)
50E	**15RBA2-50E**	1, 2	**15RBT2-50E**	3, 4	1.1 (0.5)
65E	**15RBA2-65E**	1, 2	**15RBT2-65E**	3, 4	1.1 (0.5)
80E	**15RBA2-80E**	1, 2	**15RBT2-80E**	3, 4	1.1 (0.5)
100E	**15RBA2-100E**	1, 2	**15RBT2-100E**	3, 4	1.1 (0.5)
125E	**15RBA2-125E**	1, 2	**15RBT2-125E**	3, 4	1.1 (0.5)
150E	**15RBA2-150E**	1, 2	**15RBT2-150E**	3, 4	1.1 (0.5)
200E	**15RBA2-200E**	1, 2	**15RBT2-200E**	3, 4	1.1 (0.5)

Type RBA Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 200A (For Use with 15RBA2 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Non-disconnect	**15RBA2-NH**	**15RBA2-INH**	13.8	15.5	95	**14RBA2-PNM**	**14RBA2-GNM**	**15RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**
	Non-disconnect	**15RBA2-NH**	**15RBA2-INH**	13.8	15.5	110	**15RBA2-PNM**	—	**15RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**
	Disconnect	**15RBA2-DH**	**15RBA2-IDH**	13.8	15.5	95	**14RBA2-PDM**	**14RBA2-GDM**	**38RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**
	Disconnect	**15RBA2-DH**	**15RBA2-IDH**	13.8	15.5	110	**15RBA2-PDM**	—	**38RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**
	Bolt-in	—	**15RBA2-INH-B**	13.8	15.5	95	**14RBA8-PNM**	**14RBA8-GNM**	**15RBA8-NL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**
	Bolt-in	—	**15RBA2-INH-B**	13.8	15.5	110	**15RBA8-PNM**	**15RBA8-GNM**	**15RBA8-NL**	**RBA2-FLTR** **RBA2-COND**	**15RBA2-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 200A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Dropout	**15RDB2-DH**	13.8	15.5	110	**15RDB2-VM**	**15RDB2-UM**	**RDB2-VL**	**RDB2-UL**	**15RDB2-SHNT**
	Dropout	**15RDB2-DH**	13.8	15.5	150	**15RDB2-HVM**	**15RDB2-HUM**	**RDB2-VL**	**RDB2-UL**	**15RDB2-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 15RBA4 Expulsion Fuse Refill Units—15.5 kV Maximum (14.4 kV Nominal) 400A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
0.5	**15RBA4-.5**	5, 6	—	—	2.3 (1.0)
3	**15RBA4-3**	5, 6	—	—	2.3 (1.0)
5E	**15RBA4-5E**	5, 6	—	—	2.3 (1.0)
7E	**15RBA4-7E**	5, 6	—	—	2.3 (1.0)
10E	**15RBA4-10E**	5,6	—	—	2.3 (1.0)
15E	**15RBA4-15E**	5, 6	—	—	2.3 (1.0)
20E	**15RBA4-20E**	5, 6	**15RBT4-20E**	7, 8	2.3 (1.0)
25E	**15RBA4-25E**	5, 6	**15RBT4-25E**	7, 8	2.3 (1.0)
30E	**15RBA4-30E**	5, 6	**15RBT4-30E**	7, 8	2.3 (1.0)
40E	**15RBA4-40E**	5, 6	**15RBT4-40E**	7, 8	2.3 (1.0)
50E	**15RBA4-50E**	5, 6	**15RBT4-50E**	7, 8	2.3 (1.0)
65E	**15RBA4-65E**	5, 6	**15RBT4-65E**	7, 8	2.3 (1.0)
80E	**15RBA4-80E**	5, 6	**15RBT4-80E**	7, 8	2.3 (1.0)
100E	**15RBA4-100E**	5, 6	**15RBT4-100E**	7, 8	2.3 (1.0)
125E	**15RBA4-125E**	5, 6	**15RBT4-125E**	7, 8	2.3 (1.0)
150E	**15RBA4-150E**	5, 6	**15RBT4-150E**	7, 8	2.3 (1.0)
200E	**15RBA4-200E**	5, 6	**15RBT4-200E**	7, 8	2.3 (1.0)
250E	**15RBA4-250E**	5, 6	**15RBT4-250E**	10, 11	2.3 (1.0)
300E	**15RBA4-300E**	5, 6	**15RBT4-300E**	10, 11	2.3 (1.0)
400E	**15RBA4-400E**	5, 6	**15RBT4-400E**	10, 11	2.3 (1.0)

Type RBA Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 400A (For Use with 15RBA4 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–400E	Non-disconnect	**15RBA4-NH**	**15RBA4-INH**	13.8	15.5	95	**14RBA4-PNM**	**14RBA4-GNM**	**15RBA4-NL**	**RBA4-FLTR** **RBA4-COND**	**15RBA4-SHNT**
	Non-disconnect	**15RBA4-NH**	**15RBA4-INH**	13.8	15.5	110	**15RBA4-PNM**	—	**15RBA4-NL**	**RBA4-FLTR** **RBA4-COND**	**15RBA4-SHNT**
	Disconnect	**15RBA4-DH**	**15RBA2-IDH**	13.8	15.5	95	**14RBA4-PDM**	**14RBA4-GDM**	**15RBA4-DL**	**RBA4-FLTR** **RBA4-COND**	**15RBA4-SHNT**
	Disconnect	**15RBA4-DH**	**15RBA2-IDH**	13.8	15.5	110	**15RBA4-PDM**	—	**15RBA4-DL**	**RBA4-FLTR** **RBA4-COND**	**15RBA4-SHNT**
	Bolt-in	—	**15RBA4-INH-B**	13.8	15.5	95	**14RBA8-PNM**	**14RBA8-GNM**	**15RBA8-NL**	**RBA-FLTR** **RBA4-COND**	**15RBA4-SHNT**
	Bolt-in	—	**15RBA4-INH-B**	13.8	15.5	110	**15RBA8-PNM**	**15RBA8-GNM**	**15RBA8-NL**	**RBA-FLTR** **RBA4-COND**	**15RBA4-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 400A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–400E	Dropout	**15RDB4-DH**	13.8	15.5	110	**15RDB4-VM**	**15RDB4-UM**	**RDB4-VL**	**RDB4-UL**	**15RDB4-SHNT**
	Dropout	**15RDB4-DH**	13.8	15.5	150	**15RDB4-HVM**	**15RDB4-HUM**	**RDB4-VL**	**RDB4-UL**	**15RDB4-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 15RBA4 Expulsion Fuse Refill Units Used in 15RBA8/15RDB4 Fuseholders—15.5 kV Maximum (14.4 kV Nominal) 800A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
450E	2	**15RBA4-250E**	9	2	**15RBT4-250E**	12	①
540E	2	**15RBA4-300E**	9	2	**15RBT4-300E**	12	①
720E	2	**15RBA4-400E**	9	2	**15RBT4-400E**	12	①

Type RBA Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 800A (For Use with 15RBA8 Fuseholders) ②

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
450E–720E	Non-disconnect	**15RBA8-NH**	**15RBA8-INH**	13.8	15.5	95	**14RBA8-PNM**	**14RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**15RBA4-SHNT**
	Non-disconnect	**15RBA8-NH**	**15RBA8-INH**	13.8	15.5	110	**15RBA8-PNM**	**14RBA8-GNM**	**15RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**15RBA4-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—15.5 kV Maximum (14.4 kV Nominal) 800A ④

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
450E–720E	Disconnect	**15RDB4-NH**	13.8	15.5	110	**15RDB8-VM**	**15RDB8-UM**	**RDB8-VL**	**RDB8-UL**	**15RDB4-SHNT**
	Disconnect	**15RDB4-NH**	13.8	15.5	150	**15RDB8-HVM**	**15RDB8-HUM**	**RDB8-VL**	**RDB8-UL**	**15RDB4-SHNT**

Notes

① Requires two fuse refills as shown. Price each refill individually. Example: To order refill units for a 720E, 15 kV fuse, order two pieces of an 8RBA4-400E.

② For new installation, order two refills (Standard or Time Lag), one fuseholder, one mounting, and two filters or condensers per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

③ Two filters or condensers required.

④ For new installation, order two refills (Standard or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 25RBA2 Expulsion Fuse Refill Units—25.5 kV Maximum (23.0 kV Nominal) 200A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
10E	**25RBA2-10E**	1, 2	—	—	1.3 (0.6)
15E	**25RBA2-15E**	1, 2	—	—	1.3 (0.6)
20E	**25RBA2-20E**	1, 2	**25RBT2-20E**	3, 4	1.3 (0.6)
25E	**25RBA2-25E**	1, 2	**25RBT2-25E**	3, 4	1.3 (0.6)
30E	**25RBA2-30E**	1, 2	**25RBT2-30E**	3, 4	1.3 (0.6)
40E	**25RBA2-40E**	1, 2	**25RBT2-40E**	3, 4	1.3 (0.6)
50E	**25RBA2-50E**	1, 2	**25RBT2-50E**	3, 4	1.3 (0.6)
65E	**25RBA2-65E**	1, 2	**25RBT2-65E**	3, 4	1.3 (0.6)
80E	**25RBA2-80E**	1, 2	**25RBT2-80E**	3, 4	1.3 (0.6)
100E	**25RBA2-100E**	1, 2	**25RBT2-100E**	3, 4	1.3 (0.6)
125E	**25RBA2-125E**	1, 2	**25RBT2-125E**	3, 4	1.3 (0.6)
150E	**25RBA2-150E**	1, 2	**25RBT2-150E**	3, 4	1.3 (0.6)
200E	**25RBA2-200E**	1, 2	**25RBT2-200E**	3, 4	1.3 (0.6)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—25.5 kV Maximum (23.0 kV Nominal) 200A (For Use with 25RBA2 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Non-disconnect	**25RBA2-NH**	**25RBA2-INH**	23.0	25.5	150	**25RBA2-PNM**	—	**38RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**25RBA2-SHNT**
	Non-disconnect	**25RBA2-NH**	**25RBA2-INH**	23.0	25.5	150	**25RBA2-PNM**	—	**38RBA2-NL**	**RBA2-FLTR** **RBA2-COND**	**25RBA2-SHNT**
	Disconnect	**25RBA2-DH**	**25RBA2-IDH**	23.0	25.5	150	**25RBA2-PDM**	—	**38RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**25RBA2-SHNT**
	Disconnect	**25RBA2-DH**	**25RBA2-IDH**	23.0	25.5	150	**25RBA2-PDM**	—	**38RBA2-DL**	**RBA2-FLTR** **RBA2-COND**	**25RBA2-SHNT**
	Bolt-in	—	**25RBA2-INH-B**	23.0	25.5	150	**25RBA8-PNM**	**24RBA8-GNM**	**38RBA8-NL**	**RBA2-FLTR** **RBA2-COND**	**25RBA2-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—25.5 kV Maximum (23.0 kV Nominal) 200A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Dropout	**25RDB2-DH**	23.0	25.5	150	**25RDB2-VM**	**25RDB2-UM**	**RDB2-VL**	**RDB2-UL**	**25RDB2-SHNT**
	Dropout	**25RDB2-DH**	23.0	25.5	200	**25RDB2-HVM**	**25RDB2-HUM**	**RDB2-VL**	**RDB2-UL**	**25RDB2-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 25RBA4 Expulsion Fuse Refill Units—25.5 kV Maximum (23.0 kV Nominal) 400A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
0.5	**25RBA4-.5**	5, 6	—	—	2.7 (1.2)
3	**25RBA4-3**	5, 6	—	—	2.7 (1.2)
5E	**25RBA4-5E**	5, 6	—	—	2.7 (1.2)
7E	**25RBA4-7E**	5, 6	—	—	2.7 (1.2)
10E	**25RBA4-10E**	5,6	—	—	2.7 (1.2)
15E	**25RBA4-15E**	5, 6	—	—	2.7 (1.2)
20E	**25RBA4-20E**	5, 6	**25RBT4-20E**	7, 8	2.7 (1.2)
25E	**25RBA4-25E**	5, 6	**25RBT4-25E**	7, 8	2.7 (1.2)
30E	**25RBA4-30E**	5, 6	**25RBT4-30E**	7, 8	2.7 (1.2)
40E	**25RBA4-40E**	5, 6	**25RBT4-40E**	7, 8	2.7 (1.2)
50E	**25RBA4-50E**	5, 6	**25RBT4-50E**	7, 8	2.7 (1.2)
65E	**25RBA4-65E**	5, 6	**25RBT4-65E**	7, 8	2.7 (1.2)
80E	**25RBA4-80E**	5, 6	**25RBT4-80E**	7, 8	2.7 (1.2)
100E	**25RBA4-100E**	5, 6	**25RBT4-100E**	7, 8	2.7 (1.2)
125E	**25RBA4-125E**	5, 6	**25RBT4-125E**	7, 8	2.7 (1.2)
150E	**25RBA4-150E**	5, 6	**25RBT4-150E**	7, 8	2.7 (1.2)
200E	**25RBA4-200E**	5, 6	**25RBT4-200E**	7, 8	2.7 (1.2)
250E	**25RBA4-250E**	5, 6	**25RBT4-250E**	10, 11	2.7 (1.2)
300E	**25RBA4-300E**	5, 6	**25RBT4-300E**	10, 11	2.7 (1.2)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—25.5 kV Maximum (23.0 kV Nominal) 400A (For Use with 25RBA4 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–300E	Non-disconnect	**25RBA4-NH**	**25RBA4-INH**	23.0	25.5	150	**25RBA4-PNM**	—	**38RBA4-NL**	**RBA4-FLTR**	**25RBA4-SHNT**
										RBA4-COND	
	Non-disconnect	**25RBA4-NH**	**25RBA4-INH**	23.0	25.5	150	**25RBA4-PNM**	—	**38RBA4-NL**	**RBA4-FLTR**	**25RBA4-SHNT**
										RBA4-COND	
	Disconnect	**25RBA4-DH**	**25RBA2-IDH**	23.0	25.5	150	**25RBA4-PDM**	—	**38RBA4-DL**	**RBA4-FLTR**	**25RBA4-SHNT**
										RBA4-COND	
	Disconnect	**25RBA4-DH**	**25RBA2-IDH**	23.0	25.5	150	**25RBA4-PDM**	—	**38RBA4-DL**	**RBA4-FLTR**	**25RBA4-SHNT**
										RBA4-COND	
	Bolt-in	—	**25RBA4-INH-B**	23.0	25.5	150	**25RBA8-PNM**	**25RBA8-GNM**	**38RBA8-NL**	**RBA4-FLTR**	**25RBA4-SHNT**
										RBA4-COND	

Type RDB Expulsion Fuses for Use Outdoors—25.5 kV Maximum (23.0 kV Nominal) 400A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–300E	Dropout	**25RDB4-DH**	23.0	25.5	150	**25RDB4-VM**	**25RDB4-UM**	**RDB4-VL**	**RDB4-UL**	**25RDB4-SHNT**
	Dropout	**25RDB4-DH**	23.0	25.5	200	**25RDB4-HVM**	**25RDB4-HUM**	**RDB4-VL**	**RDB4-UL**	**25RDB4-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase.
Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase.
Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 25RBA4 Expulsion Fuse Refill Units Used in 25RBA8/15RDB4 Fuseholders—25.5 kV Maximum (23.0 kV Nominal) 800A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Quantity	Standard Speed (Fuse Refills) Catalog Number	Standard Speed (Fuse Refills) Curve Reference 36-635	Time Lag (Fuse Refills) Quantity	Time Lag (Fuse Refills) Catalog Number	Time Lag (Fuse Refills) Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
450E	2	**25RBA4-250E**	9	2	**25RBT4-250E**	12	①
540E	2	**25RBA4-300E**	9	2	**25RBT4-300E**	12	①

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—25.5 kV Maximum (23.0 kV Nominal) 800A (For Use with 25RBA8 Fuseholders) ②

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
450E–540E	Non-disconnect	**25RBA8-NH**	**25RBA8-INH**	23.0	25.5	150	**25RBA8-PNM**	—	**38RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**25RBA4-SHNT**
	Non-disconnect	**25RBA8-NH**	**25RBA8-INH**	23.0	25.5	150	**25RBA8-PNM**	—	**38RBA8-NL**	**RBA4-FLTR** ③ **RBA4-COND** ③	**25RBA4-SHNT**

Type RDB Expulsion Fuses for Use Outdoors—25.5 kV Maximum (23.0 kV Nominal) 800A ④

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
450E–540E	Disconnect	**25RDB4-NH**	23.0	25.5	150	**25RDB8-VM**	**25RDB8-UM**	**RDB8-VL**	**RDB8-UL**	**25RDB4-SHNT**
	Disconnect	**25RDB4-NH**	23.0	25.5	200	**25RDB8-HVM**	**25RDB8-HUM**	**RDB8-VL**	**RDB8-UL**	**25RDB4-SHNT**

Notes

① Requires two fuse refills as shown. Price each refill individually. Example: To order refill units for a 720E, 25 kV fuse, order two pieces of an 8RBA4-400E.

② For new installation, order two refills (Standard or Time Lag), one fuseholder, one mounting, and two filters or condensers per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

③ Two filters or condensers required.

④ For new installation, order two refills (Standard or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 38RBA2 Expulsion Fuse Refill Units—38.0 kV Maximum (34.5 kV Nominal) 200A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
10E	**38RBA2-10E**	1, 2	—	—	1.4 (0.6)
15E	**38RBA2-15E**	1, 2	—	—	1.4 (0.6)
20E	**38RBA2-20E**	1, 2	**38RBT2-20E**	3, 4	1.4 (0.6)
25E	**38RBA2-25E**	1, 2	**38RBT2-25E**	3, 4	1.4 (0.6)
30E	**38RBA2-30E**	1, 2	**38RBT2-30E**	3, 4	1.4 (0.6)
40E	**38RBA2-40E**	1, 2	**38RBT2-40E**	3, 4	1.4 (0.6)
50E	**38RBA2-50E**	1, 2	**38RBT2-50E**	3, 4	1.4 (0.6)
65E	**38RBA2-65E**	1, 2	**38RBT2-65E**	3, 4	1.4 (0.6)
80E	**38RBA2-80E**	1, 2	**38RBT2-80E**	3, 4	1.4 (0.6)
100E	**38RBA2-100E**	1, 2	**38RBT2-100E**	3, 4	1.4 (0.6)
125E	**38RBA2-125E**	1, 2	**38RBT2-125E**	3, 4	1.4 (0.6)
150E	**38RBA2-150E**	1, 2	**38RBT2-150E**	3, 4	1.4 (0.6)
200E	**38RBA2-200E**	1, 2	**38RBT2-200E**	3, 4	1.4 (0.6)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—38.0 kV Maximum (34.5 kV Nominal) 200A (For Use with 38RBA2 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Non-disconnect	**38RBA2-NH**	**38RBA2-INH**	34.5	38.0	150	**38RBA2-PNM**	—	**38RBA2-NL**	**RBA2-FLTR**	**38RBA2-SHNT**
										RBA2-COND	
	Non-disconnect	**38RBA2-NH**	**38RBA2-INH**	34.5	38.0	150	**38RBA2-PNM**	—	**38RBA2-NL**	**RBA2-FLTR**	**38RBA2-SHNT**
										RBA2-COND	
	Disconnect	**38RBA2-DH**	**38RBA2-IDH**	34.5	38.0	150	**38RBA2-PDM**	—	**38RBA2-DL**	**RBA2-FLTR**	**38RBA2-SHNT**
										RBA2-COND	
	Disconnect	**38RBA2-DH**	**38RBA2-IDH**	34.5	38.0	150	**38RBA2-PDM**	—	**38RBA2-DL**	**RBA2-FLTR**	**38RBA2-SHNT**
										RBA2-COND	
	Bolt-in	—	**38RBA2-INH-B**	34.5	38.0	150	**38RBA8-PNM**	**38RBA8-GNM**	**38RBA8-NL**	**RBA2-FLTR**	**38RBA2-SHNT**
										RBA2-COND	

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—38.0 kV Maximum (34.5 kV Nominal) 200A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
10E–200E	Dropout	**38RDB2-DH**	34.5	38.0	200	**38RDB2-VM**	**38RDB2-UM**	**RDB2-VL**	**RDB2-UL**	**38RDB2-SHNT**
	Dropout	**38RDB2-DH**	34.5	38.0	250	**38RDB2-HVM**	**38RDB2-HUM**	**RDB2-VL**	**RDB2-UL**	**38RDB2-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 38RBA4 Expulsion Fuse Refill Units—38.0 kV Maximum (34.5 kV Nominal) 400A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Catalog Number	Standard Speed (Fuse Refills) Curve Reference 36-635	Time Lag (Fuse Refills) Catalog Number	Time Lag (Fuse Refills) Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
0.5	**38RBA4-.5**	5, 6	—	—	3.1 (1.4)
3	**38RBA4-3**	5, 6	—	—	3.1 (1.4)
5E	**38RBA4-5E**	5, 6	—	—	3.1 (1.4)
7E	**38RBA4-7E**	5, 6	—	—	3.1 (1.4)
10E	**38RBA4-10E**	5,6	—	—	3.1 (1.4)
15E	**38RBA4-15E**	5, 6	—	—	3.1 (1.4)
20E	**38RBA4-20E**	5, 6	**38RBT4-20E**	7, 8	3.1 (1.4)
25E	**38RBA4-25E**	5, 6	**38RBT4-25E**	7, 8	3.1 (1.4)
30E	**38RBA4-30E**	5, 6	**38RBT4-30E**	7, 8	3.1 (1.4)
40E	**38RBA4-40E**	5, 6	**38RBT4-40E**	7, 8	3.1 (1.4)
50E	**38RBA4-50E**	5, 6	**38RBT4-50E**	7, 8	3.1 (1.4)
65E	**38RBA4-65E**	5, 6	**38RBT4-65E**	7, 8	3.1 (1.4)
80E	**38RBA4-80E**	5, 6	**38RBT4-80E**	7, 8	3.1 (1.4)
100E	**38RBA4-100E**	5, 6	**38RBT4-100E**	7, 8	3.1 (1.4)
125E	**38RBA4-125E**	5, 6	**38RBT4-125E**	7, 8	3.1 (1.4)
150E	**38RBA4-150E**	5, 6	**38RBT4-150E**	7, 8	3.1 (1.4)
200E	**38RBA4-200E**	5, 6	**38RBT4-200E**	7, 8	3.1 (1.4)
250E	**38RBA4-250E**	5, 6	**38RBT4-250E**	10, 11	3.1 (1.4)
300E	**38RBA4-300E**	5, 6	**38RBT4-300E**	(0, 11	3.1 (1.4)

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure— 38.0 kV Maximum (34.5 kV Nominal) 400A (For Use with 38RBA4 Fuseholders) ①

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–300E	Non-disconnect	**38RBA4-NH**	**38RBA4-INH**	34.5	38.0	150	**38RBA4-PNM**	—	**38RBA4-NL**	**RBA4-FLTR**	**38RBA4-SHNT**
										RBA4-COND	
	Non-disconnect	**38RBA4-NH**	**38RBA4-INH**	34.5	38.0	150	**38RBA4-PNM**	—	**38RBA4-NL**	**RBA4-FLTR**	**38RBA4-SHNT**
										RBA4-COND	
	Disconnect	**38RBA4-DH**	**38RBA2-IDH**	34.5	38.0	150	**38RBA4-PDM**	—	**38RBA4-DL**	**RBA4-FLTR**	**38RBA4-SHNT**
										RBA4-COND	
	Disconnect	**38RBA4-DH**	**38RBA2-IDH**	34.5	38.0	150	**38RBA4-PDM**	—	**38RBA4-DL**	**RBA4-FLTR**	**38RBA4-SHNT**
										RBA4-COND	
	Bolt-in	—	**38RBA4-INH-B**	34.5	38.0	150	**38RBA8-PNM**	**38RBA8-GNM**	**38RBA8-NL**	**RBA4-FLTR**	**38RBA4-SHNT**
										RBA4-COND	

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—38.0 kV Maximum (34.5 kV Nominal) 400A ②

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
0.5–300E	Dropout	**38RDB4-DH**	34.5	38.0	150	**38RDB4-VM**	**38RDB4-UM**	**RDB4-VL**	**RDB4-UL**	**38RDB4-SHNT**
	Dropout	**38RDB4-DH**	34.5	38.0	200	**38RDB4-HVM**	**38RDB4-HUM**	**RDB4-VL**	**RDB4-UL**	**38RDB4-SHNT**

Notes

① For new installation, order one refill (Standard Speed or Time Lag), one fuseholder, one mounting, and one filter or condenser per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

② For new installation, order one refill (Standard Speed or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type 38RBA4 Expulsion Fuse Refill Units Used in 38RBA8/15RDB4 Fuseholders—38.0 kV Maximum (34.5 kV Nominal) 800A

RBA/RBT Refill Units

Ampere Rating	Standard Speed (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Time Lag (Fuse Refills) Quantity	Catalog Number	Curve Reference 36-635	Approximate Shipping Weight Lbs (kg)
450E	2	**38RBA4-250E**	9	2	**38RBT4-250E**	12	①
540E	2	**38RBA4-300E**	9	2	**38RBT4-300E**	12	①

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—38.0 kV Maximum (34.5 kV Nominal) 800A (For Use with 38RBA8 Fuseholders) ②

RBA Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Indoor or Enclosure Applications)

Ampere Rating	Style	Fuseholder Non-Indicating Catalog Number	Fuseholder Indicating Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Porcelain Insulator Catalog Number	Mounting (Including Live Parts Less Holder) Glass Polyester Catalog Number	Live Parts Catalog Number	Fuse Filters and Condensers Catalog Number	Spring and Shunt Assy. Catalog Number
450E–540E	Non-disconnect	**38RBA8-NH**	**38RBA8-INH**	34.5	38.0	150	**38RBA8-PNM**	—	**38RBA8-NL**	**RBA4-FLTR** ③	**38RBA4-SHNT**
										RBA4-COND ③	
	Non-disconnect	**38RBA8-NH**	**38RBA8-INH**	34.5	38.0	150	**38RBA8-PNM**	—	**38RBA8-NL**	**RBA4-FLTR** ③	**38RBA4-SHNT**
										RBA4-COND ③	

Type RBA Expulsion Fuses for Use Indoors or in an Enclosure—38.0 kV Maximum (34.5 kV Nominal) 800A ④

RDB Fuseholders, Mountings and Hardware (For Use with RBA/RBT Refills/Holders for Outdoor Applications)

Ampere Rating	Style	Fuseholder Catalog Number	Voltage (kV) Nominal	Voltage (kV) Maximum	LIWL (BIL)	Mounting (Including Live Parts Less Holder) Vertical (180°) Mounting Catalog Number	Mounting (Including Live Parts Less Holder) Underhung (90°) Mounting Catalog Number	Live Parts Vertical Catalog Number	Live Parts Underhung Catalog Number	Spring and Shunt Assy. Catalog Number
450E–540E	Disconnect	**38RDB4-NH**	34.5	38.0	150	**38RDB8-VM**	**38RDB8-UM**	**RDB8-VL**	**RDB8-UL**	**38RDB4-SHNT**
	Disconnect	**38RDB4-NH**	34.5	38.0	200	**38RDB8-HVM**	**38RDB8-HUM**	**RDB8-VL**	**RDB8-UL**	**38RDB4-SHNT**

Notes

① Requires two fuse refills as shown. Price each refill individually. Example: To order refill units for a 720E, 38 kV fuse, order 2 pieces of an 8RBA4-400E.

② For new installation, order two refills (Standard or Time Lag), one fuseholder, one mounting, and two filters or condensers per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

③ Two filters or condensers required.

④ For new installation, order two refills (Standard or Time Lag), one fuseholder and one mounting per phase. Live parts can be substituted for the mounting if the user is supplying base support and insulators.

Type DBU

DBU-EFID



DBU17-GNM

DBU17-GDM



DBU-EFOD



Type DBU Expulsion Fuse Units 17.1 kV Maximum, 14.4 kV Nominal

Standard Speed			Slow Speed			K Speed		
Ampere Rating	Catalog Number ①②	Curve Reference 36-643	Ampere Rating	Catalog Number ①②	Curve Reference 36-643	Ampere Rating	Catalog Number ①②	Curve Reference 36-643
5E	**DBU17-5E**	11,14	—	—	—	3K	**DBU17-3K**	12, 15
7E	**DBU17-7E**	11,14	—	—	—	6K	**DBU17-6K**	12, 15
10E	**DBU17-10E**	11,14	—	—	—	8K	**DBU17-8K**	12, 15
13E	**DBU17-13E**	11,14	—	—	—	10K	**DBU17-10K**	12, 15
15E	**DBU17-15E**	11,14	15SE	**DBU17-15SE**	10, 13	12K	**DBU17-12K**	12, 15
20E	**DBU17-20E**	11,14	20SE	**DBU17-20SE**	10, 13	15K	**DBU17-15K**	12, 15
25E	**DBU17-25E**	11,14	25SE	**DBU17-25SE**	10, 13	20K	**DBU17-20K**	12, 15
30E	**DBU17-30E**	11,14	30SE	**DBU17-30SE**	10, 13	25K	**DBU17-25K**	12, 15
40E	**DBU17-40E**	11,14	40SE	**DBU17-40SE**	10, 13	30K	**DBU17-30K**	12, 15
50E	**DBU17-50E**	11,14	50SE	**DBU17-50SE**	10, 13	40K	**DBU17-40K**	12, 15
65E	**DBU17-65E**	11,14	65SE	**DBU17-65SE**	10, 13	50K	**DBU17-50K**	12, 15
80E	**DBU17-80E**	11,14	80SE	**DBU17-80SE**	10, 13	65K	**DBU17-65K**	12, 15
100E	**DBU17-100E**	11,14	100SE	**DBU17-100SE**	10, 13	80K	**DBU17-80K**	12, 15
125E	**DBU17-125E**	11,14	125SE	**DBU17-125SE**	10, 13	100K	**DBU17-100K**	12, 15
150E	**DBU17-150E**	11,14	150SE	**DBU17-150SE**	10, 13	140K	**DBU17-140K**	12, 15
175E	**DBU17-175E**	11,14	175SE	**DBU17-175SE**	10, 13	200K	**DBU17-200K**	12, 15
200E	**DBU17-200E**	11,14	200SE	**DBU17-200SE**	10, 13	—	—	—

Type DBU Expulsion Fuse Mountings 17.1 kV Maximum, 14.4 kV Nominal

Ampere Rating	Style	Style	Voltage (kV) Nominal	Maximum	LIWL (BIL)	Mounting	Live Parts	End Fittings	Muffler
5E–200E, 15SE–200SE, 3K–200K	Indoor	Non loadbreak	13.8	17.1	95	**DBU17-GNM** ③	**DBU17-NL** ③	**DBU-EFID** ④	**DBU-MFLR**
	Indoor	Loadbreak	13.8	17.1	95	**DBU17-GDM** ③	**DBU17-DL** ③	**DBU-EFID** ④	**DBU-MFLR**
	Outdoor	Dropout	13.8	17.1	125	**DBU-17-DM**	—	**DBU-EFOD**	—

Notes

① Maximum interrupting rating 14 kA symmetrical.

② Approximate shipping weight 2.1 lb (0.95 kg).

③ To complete the mounting catalog number, specify -R for right side cale terminator or -L for left side cale terminator.

④ End fittings DBU-EFID include a muffler.

DBU-EFID



DBU17-GNM

DBU17-GDM

DBU-EFOD



Type DBU Expulsion Fuse Units 27.0 kV Maximum, 25 kV Nominal

Standard Speed			Slow Speed			K Speed		
Ampere Rating	Catalog Number ①②	Curve Reference 36-643	Ampere Rating	Catalog Number ①②	Curve Reference 36-643	Ampere Rating	Catalog Number ①②	Curve Reference 36-643
5E	**DBU27-5E**	11,17	—	**—**	—	3K	**DBU27-3K**	12, 18
7E	**DBU27-7E**	11,17	—	**—**	—	6K	**DBU27-6K**	12, 18
10E	**DBU27-10E**	11,17	—	**—**	—	8K	**DBU27-8K**	12, 18
13E	**DBU27-13E**	11,17	—	**—**	—	10K	**DBU27-10K**	12, 18
15E	**DBU27-15E**	11,17	15SE	**DBU27-15SE**	10, 16	12K	**DBU27-12K**	12, 18
20E	**DBU27-20E**	11,17	20SE	**DBU27-20SE**	10, 16	15K	**DBU27-15K**	12, 18
25E	**DBU27-25E**	11,17	25SE	**DBU27-25SE**	10, 16	20K	**DBU27-20K**	12, 18
30E	**DBU27-30E**	11,17	30SE	**DBU27-30SE**	10, 16	25K	**DBU27-25K**	12, 18
40E	**DBU27-40E**	11,17	40SE	**DBU27-40SE**	10, 16	30K	**DBU27-30K**	12, 18
50E	**DBU27-50E**	11,17	50SE	**DBU27-50SE**	10, 16	40K	**DBU27-40K**	12, 18
65E	**DBU27-65E**	11,17	65SE	**DBU27-65SE**	10, 16	50K	**DBU27-50K**	12, 18
80E	**DBU27-80E**	11,17	80SE	**DBU27-80SE**	10, 16	65K	**DBU27-65K**	12, 18
100E	**DBU27-100E**	11,17	100SE	**DBU27-100SE**	10, 16	80K	**DBU27-80K**	12, 18
125E	**DBU27-125E**	11,17	125SE	**DBU27-125SE**	10, 16	100K	**DBU27-100K**	12, 18
150E	**DBU27-150E**	11,17	150SE	**DBU27-150SE**	10, 16	140K	**DBU27-140K**	12, 18
175E	**DBU27-175E**	11,17	175SE	**DBU27-175SE**	10, 16	200K	**DBU27-200K**	12, 18
200E	**DBU27-200E**	11,17	200SE	**DBU27-200SE**	10, 16	—	**—**	—

Type DBU Expulsion Fuse Mountings 27.0 kV Maximum, 25 kV Nominal

Ampere Rating	Style	Style	Voltage (kV) Nominal	Maximum	LIWL (BIL)	Mounting	Live Parts	End Fittings	Muffler
5E–200E, 15SE–200SE, 3K–200K	Indoor	Non loadbreak	23.5	27.0	110	**DBU27-GNM** ③	**DBU27-NL** ③	**DBU-EFID** ④	**DBU-MFLR**
	Indoor	Loadbreak	23.5	27.0	110	**DBU27-GDM** ③	**DBU27-DL** ③	**DBU-EFID** ④	**DBU-MFLR**
	Outdoor	Dropout	23.5	27.0	150	**DBU-27-DM**	—	**DBU-EFOD**	—

Notes

① Maximum interrupting rating 12.5 kA symmetrical.
② Approximate shipping weight 2.1 lb (0.95 kg).
③ To complete the mounting catalog number, specify -R for right side cale terminator or -L for left side cale terminator.
④ End fittings DBU-EFID include a muffler.

DBU-EFID



DBU17-GNM

DBU17-GDM

DBU-EFOD



Type DBU Expulsion Fuse Units 38.8 kV Maximum, 34.5 kV Nominal

Standard Speed			Slow Speed			K Speed		
Ampere Rating	Catalog Number ①②	Curve Reference 36-643	Ampere Rating	Catalog Number ②	Curve Reference 36-643	Ampere Rating	Catalog Number ①②	Curve Reference 36-643
5E	**DBU38-5E**	11,17	—	**—**	—	3K	**DBU38-3K**	12, 18
7E	**DBU38-7E**	11,17	—	**—**	—	6K	**DBU38-6K**	12, 18
10E	**DBU38-10E**	11,17	—	**—**	—	8K	**DBU38-8K**	12, 18
13E	**DBU38-13E**	11,17	—	**—**	—	10K	**DBU38-10K**	12, 18
15E	**DBU38-15E**	11,17	15SE	**DBU38-15SE**	10, 16	12K	**DBU38-12K**	12, 18
20E	**DBU38-20E**	11,17	20SE	**DBU38-20SE**	10, 16	15K	**DBU38-15K**	12, 18
25E	**DBU38-25E**	11,17	25SE	**DBU38-25SE**	10, 16	20K	**DBU38-20K**	12, 18
30E	**DBU38-30E**	11,17	30SE	**DBU38-30SE**	10, 16	25K	**DBU38-25K**	12, 18
40E	**DBU38-40E**	11,17	40SE	**DBU38-40SE**	10, 16	30K	**DBU38-30K**	12, 18
50E	**DBU38-50E**	11,17	50SE	**DBU38-50SE**	10, 16	40K	**DBU38-40K**	12, 18
65E	**DBU38-65E**	11,17	65SE	**DBU38-65SE**	10, 16	50K	**DBU38-50K**	12, 18
80E	**DBU38-80E**	11,17	80SE	**DBU38-80SE**	10, 16	65K	**DBU38-65K**	12, 18
100E	**DBU38-100E**	11,17	100SE	**DBU38-100SE**	10, 16	80K	**DBU38-80K**	12, 18
125E	**DBU38-125E**	11,17	125SE	**DBU38-125SE**	10, 16	100K	**DBU38-100K**	12, 18
150E	**DBU38-150E**	11,17	150SE	**DBU38-150SE**	10, 16	140K	**DBU38-140K**	12, 18
175E	**DBU38-175E**	11,17	175SE	**DBU38-175SE**	10, 16	200K	**DBU38-200K**	12, 18
200E	**DBU38-200E**	11,17	200SE	**DBU38-200SE**	10, 16	—	**—**	—

Type DBU Expulsion Fuse Mountings 38.0 kV Maximum, 34.5 kV Nominal

Ampere Rating	Style	Style	Voltage (kV) Nominal	Maximum	LIWL (BIL)	Mounting	Live Parts	End Fittings	Muffler
5E–200E, 15SE–200SE, 3K–200K	Indoor	Non loadbreak	34.5	38	150	**DBU38-GNM** ③	**DBU38-NL** ③	**DBU-EFID** ④	**DBU-MFLR**

Notes

① Maximum interrupting rating 10 kA symmetrical (outdoor dropout, 8.5 kA indoor with muffler.

② Approximate shipping weight 2.1 lb (0.95 kg).

③ To complete the mounting catalog number, specify -R for right side cale terminator or -L for left side cale terminator.

④ End fittings DBU-EFID includes a muffler.

Technical Data and Specifications

Type DBA

Type DBA Expulsion Fuses for Use Indoors or Outdoors

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
Type DBA-1 Fuse Refills 8.3 kV Maximum (7.2 kV Nominal)			
0.5	**8DBA1-.5**	10, 11	1.5 (0.7)
3	**8DBA1-3**	10, 11	1.5 (0.7)
5E	**8DBA1-5E**	10, 11	1.5 (0.7)
7E	**8DBA1-7E**	10, 11	1.5 (0.7)
10E	**8DBA1-10E**	10, 11	1.5 (0.7)
15E	**8DBA1-15E**	10, 11	1.5 (0.7)
20E	**8DBA1-20E**	10, 11	1.5 (0.7)
25E	**8DBA1-25E**	10, 11	1.5 (0.7)
30E	**8DBA1-30E**	10, 11	1.5 (0.7)
40E	**8DBA1-40E**	10, 11	1.5 (0.7)
50E	**8DBA1-50E**	10, 11	1.5 (0.7)
65E	**8DBA1-65E**	10, 11	1.5 (0.7)
80E	**8DBA1-80E**	10, 11	1.5 (0.7)
100E	**8DBA1-100E**	10, 11	1.5 (0.7)
125E	**8DBA1-125E**	10, 11	1.5 (0.7)
150E	**8DBA1-150E**	10, 11	1.5 (0.7)
200E	**8DBA1-200E**	10, 11	1.5 (0.7)
15.5 kV Maximum (14.4 kV Nominal)			
0.5	**15DBA1-.5**	10, 11	2.1 (0.95)
3	**15DBA1-3**	10, 11	2.1 (0.95)
5E	**15DBA1-5E**	10, 11	2.1 (0.95)
7E	**15DBA1-7E**	10, 11	2.1 (0.95)
10E	**15DBA1-10E**	10, 11	2.1 (0.95)
15E	**15DBA1-15E**	10, 11	2.1 (0.95)
20E	**15DBA1-20E**	10, 11	2.1 (0.95)
25E	**15DBA1-25E**	10, 11	2.1 (0.95)
30E	**15DBA1-30E**	10, 11	2.1 (0.95)
40E	**15DBA1-40E**	10, 11	2.1 (0.95)
50E	**15DBA1-50E**	10, 11	2.1 (0.95)
65E	**15DBA1-65E**	10, 11	2.1 (0.95)
80E	**15DBA1-80E**	10, 11	2.1 (0.95)
100E	**15DBA1-100E**	10, 11	2.1 (0.95)
125E	**15DBA1-125E**	10, 11	2.1 (0.95)
150E	**15DBA1-150E**	10, 11	2.1 (0.95)
200E	**15DBA1-200E**	10, 11	2.1 (0.95)

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
25 kV Maximum (23 kV Nominal)			
0.5	**25DBA1-.5**	10, 11	3.1 (1.4)
3	**25DBA1-3**	10, 11	3.1 (1.4)
5E	**25DBA1-5E**	10, 11	3.1 (1.4)
7E	**25DBA1-7E**	10, 11	3.1 (1.4)
10E	**25DBA1-10E**	10, 11	3.1 (1.4)
15E	**25DBA1-15E**	10, 11	3.1 (1.4)
20E	**25DBA1-20E**	10, 11	3.1 (1.4)
25E	**25DBA1-25E**	10, 11	3.1 (1.4)
30E	**25DBA1-30E**	10, 11	3.1 (1.4)
40E	**25DBA1-40E**	10, 11	3.1 (1.4)
50E	**25DBA1-50E**	10, 11	3.1 (1.4)
65E	**25DBA1-65E**	10, 11	3.1 (1.4)
80E	**25DBA1-80E**	10, 11	3.1 (1.4)
100E	**25DBA1-100E**	10, 11	3.1 (1.4)
125E	**25DBA1-125E**	10, 11	3.1 (1.4)
150E	**25DBA1-150E**	10, 11	3.1 (1.4)
200E	**25DBA1-200E**	10, 11	3.1 (1.4)

Type DBA Expulsion Fuses for Use Indoors or Outdoors, continued

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
Type DBA-1 Fuse Refills 38 kV Maximum (34.5 kV Nominal)			
0.5	**38DBA1-.5**	10, 12	4.2 (1.9)
3	**38DBA1-3**	10, 12	4.2 (1.9)
5E	**38DBA1-5E**	10, 12	4.2 (1.9)
7E	**38DBA1-7E**	10, 12	4.2 (1.9)
10E	**38DBA1-10E**	10, 12	4.2 (1.9)
15E	**38DBA1-15E**	10, 12	4.2 (1.9)
20E	**38DBA1-20E**	10, 12	4.2 (1.9)
25E	**38DBA1-25E**	10, 12	4.2 (1.9)
30E	**38DBA1-30E**	10, 12	4.2 (1.9)
40E	**38DBA1-40E**	10, 12	4.2 (1.9)
50E	**38DBA1-50E**	10, 12	4.2 (1.9)
65E	**38DBA1-65E**	10, 12	4.2 (1.9)
80E	**38DBA1-80E**	10, 12	4.2 (1.9)
100E	**38DBA1-100E**	10, 12	4.2 (1.9)
125E	**38DBA1-125E**	10, 12	4.2 (1.9)
150E	**38DBA1-150E**	10, 12	4.2 (1.9)
200E	**38DBA1-200E**	10, 12	4.2 (1.9)
48 kV Maximum (46 kV Nominal)			
0.5	**48DBA1-.5**	10, 12	6.5 (3.0)
3	**48DBA1-3**	10, 12	6.5 (3.0)
5E	**48DBA1-5E**	10, 12	6.5 (3.0)
7E	**48DBA1-7E**	10, 12	6.5 (3.0)
10E	**48DBA1-10E**	10, 12	6.5 (3.0)
15E	**48DBA1-15E**	10, 12	6.5 (3.0)
20E	**48DBA1-20E**	10, 12	6.5 (3.0)
25E	**48DBA1-25E**	10, 12	6.5 (3.0)
30E	**48DBA1-30E**	10, 12	6.5 (3.0)
40E	**48DBA1-40E**	10, 12	6.5 (3.0)
50E	**48DBA1-50E**	10, 12	6.5 (3.0)
65E	**48DBA1-65E**	10, 12	6.5 (3.0)
80E	**48DBA1-80E**	10, 12	6.5 (3.0)
100E	**48DBA1-100E**	10, 12	6.5 (3.0)
125E	**48DBA1-125E**	10, 12	6.5 (3.0)
150E	**48DBA1-150E**	10, 12	6.5 (3.0)
200E	**48DBA1-200E**	10, 12	6.5 (3.0)

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
72 kV Maximum (69 kV Nominal)			
0.5	**72DBA1-.5**	10, 12	7.1 (3.2)
3	**72DBA1-3**	10, 12	7.1 (3.2)
5E	**72DBA1-5E**	10, 12	7.1 (3.2)
7E	**72DBA1-7E**	10, 12	7.1 (3.2)
10E	**72DBA1-10E**	10, 12	7.1 (3.2)
15E	**72DBA1-15E**	10, 12	7.1 (3.2)
20E	**72DBA1-20E**	10, 12	7.1 (3.2)
25E	**72DBA1-25E**	10, 12	7.1 (3.2)
30E	**72DBA1-30E**	10, 12	7.1 (3.2)
40E	**72DBA1-40E**	10, 12	7.1 (3.2)
50E	**72DBA1-50E**	10, 12	7.1 (3.2)
65E	**72DBA1-65E**	10, 12	7.1 (3.2)
80E	**72DBA1-80E**	10, 12	7.1 (3.2)
100E	**72DBA1-100E**	10, 12	7.1 (3.2)
125E	**72DBA1-125E**	10, 12	7.1 (3.2)
150E	**72DBA1-150E**	10, 12	7.1 (3.2)
200E	**72DBA1-200E**	10, 12	7.1 (3.2)

Type DBA Expulsion Fuses for Use Indoors or Outdoors, continued

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
Type DBA-2 Fuse Refills 38 kV Maximum (34.5 kV Nominal)			
0.5	**38DBA2-.5**	10, 12	10 (4.5)
3	**38DBA2-3**	10, 12	10 (4.5)
5E	**38DBA2-5E**	10, 12	10 (4.5)
7E	**38DBA2-7E**	10, 12	10 (4.5)
10E	**38DBA2-10E**	10, 12	10 (4.5)
15E	**38DBA2-15E**	10, 12	10 (4.5)
20E	**38DBA2-20E**	10, 12	10 (4.5)
25E	**38DBA2-25E**	10, 12	10 (4.5)
30E	**38DBA2-30E**	10, 12	10 (4.5)
40E	**38DBA2-40E**	10, 12	10 (4.5)
50E	**38DBA2-50E**	10, 12	10 (4.5)
65E	**38DBA2-65E**	10, 12	10 (4.5)
80E	**38DBA2-80E**	10, 12	10 (4.5)
100E	**38DBA2-100E**	10, 12	10 (4.5)
125E	**38DBA2-125E**	10, 12	10 (4.5)
150E	**38DBA2-150E**	10, 12	10 (4.5)
200E	**38DBA2-200E**	10, 12	10 (4.5)
48 kV Maximum (46 kV Nominal)			
0.5	**48DBA2-.5**	10, 12	12 (5.4)
3	**48DBA2-3**	10, 12	12 (5.4)
5E	**48DBA2-5E**	10, 12	12 (5.4)
7E	**48DBA2-7E**	10, 12	12 (5.4)
10E	**48DBA2-10E**	10, 12	12 (5.4)
15E	**48DBA2-15E**	10, 12	12 (5.4)
20E	**48DBA2-20E**	10, 12	12 (5.4)
25E	**48DBA2-25E**	10, 12	12 (5.4)
30E	**48DBA2-30E**	10, 12	12 (5.4)
40E	**48DBA2-40E**	10, 12	12 (5.4)
50E	**48DBA2-50E**	10, 12	12 (5.4)
65E	**48DBA2-65E**	10, 12	12 (5.4)
80E	**48DBA2-80E**	10, 12	12 (5.4)
100E	**48DBA2-100E**	10, 12	12 (5.4)
125E	**48DBA2-125E**	10, 12	12 (5.4)
150E	**48DBA2-150E**	10, 12	12 (5.4)
200E	**48DBA2-200E**	10, 12	12 (5.4)

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
72 kV Maximum (69 kV Nominal)			
0.5	**72DBA2-.5**	10, 12	15 (6.8)
3	**72DBA2-3**	10, 12	15 (6.8)
5E	**72DBA2-5E**	10, 12	15 (6.8)
7E	**72DBA2-7E**	10, 12	15 (6.8)
10E	**72DBA2-10E**	10, 12	15 (6.8)
15E	**72DBA2-15E**	10, 12	15 (6.8)
20E	**72DBA2-20E**	10, 12	15 (6.8)
25E	**72DBA2-25E**	10, 12	15 (6.8)
30E	**72DBA2-30E**	10, 12	15 (6.8)
40E	**72DBA2-40E**	10, 12	15 (6.8)
50E	**72DBA2-50E**	10, 12	15 (6.8)
65E	**72DBA2-65E**	10, 12	15 (6.8)
80E	**72DBA2-80E**	10, 12	15 (6.8)
100E	**72DBA2-100E**	10, 12	15 (6.8)
125E	**72DBA2-125E**	10, 12	15 (6.8)
150E	**72DBA2-150E**	10, 12	15 (6.8)
200E	**72DBA2-200E**	10, 12	15 (6.8)

Type DBA Expulsion Fuses for Use Indoors or Outdoors, continued

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
Type DBA-2 Fuse Refills 92 kV Maximum (92 kV Nominal)			
3	**92DBA2-3**	10, 13	19 (8.6)
5E	**92DBA2-5E**	10, 13	19 (8.6)
7E	**92DBA2-7E**	10, 13	19 (8.6)
10E	**92DBA2-10E**	10, 13	19 (8.6)
15E	**92DBA2-15E**	10, 13	19 (8.6)
20E	**92DBA2-20E**	10, 13	19 (8.6)
25E	**92DBA2-25E**	10, 13	19 (8.6)
30E	**92DBA2-30E**	10, 13	19 (8.6)
40E	**92DBA2-40E**	10, 13	19 (8.6)
50E	**92DBA2-50E**	10, 13	19 (8.6)
65E	**92DBA2-65E**	10, 13	19 (8.6)
80E	**92DBA2-80E**	10, 13	19 (8.6)
100E	**92DBA2-100E**	10, 13	19 (8.6)
125E	**92DBA2-125E**	10, 13	19 (8.6)
150E	**92DBA2-150E**	10, 13	19 (8.6)
200E	**92DBA2-200E**	10, 13	19 (8.6)
121 kV Maximum (115 kV Nominal)			
3	**121DBA2-3**	10, 13	22 (10)
5E	**121DBA2-5E**	10, 13	22 (10)
7E	**121DBA2-7E**	10, 13	22 (10)
10E	**121DBA2-10E**	10, 13	22 (10)
15E	**121DBA2-15E**	10, 13	22 (10)
20E	**121DBA2-20E**	10, 13	22 (10)
25E	**121DBA2-25E**	10, 13	22 (10)
30E	**121DBA2-30E**	10, 13	22 (10)
40E	**121DBA2-40E**	10, 13	22 (10)
50E	**121DBA2-50E**	10, 13	22 (10)
65E	**121DBA2-65E**	10, 13	22 (10)
80E	**121DBA2-80E**	10, 13	22 (10)
100E	**121DBA2-100E**	10, 13	22 (10)
125E	**121DBA2-125E**	10, 13	22 (10)
150E	**121DBA2-150E**	10, 13	22 (10)
200E	**121DBA2-200E**	10, 13	22 (10)

Ampere Rating	DBA-1 Fuse Units Catalog Number	Curve Reference 36-623	Approximate Shipping Weight Lbs (kg)
145 kV Maximum (138 kV Nominal)			
3	**145DBA2-3**	10, 13	25 (11.4)
5E	**145DBA2-5E**	10, 13	25 (11.4)
7E	**145DBA2-7E**	10, 13	25 (11.4)
10E	**145DBA2-10E**	10, 13	25 (11.4)
15E	**145DBA2-15E**	10, 13	25 (11.4)
20E	**145DBA2-20E**	10, 13	25 (11.4)
25E	**145DBA2-25E**	10, 13	25 (11.4)
30E	**145DBA2-30E**	10, 13	25 (11.4)
40E	**145DBA2-40E**	10, 13	25 (11.4)
50E	**145DBA2-50E**	10, 13	25 (11.4)
65E	**145DBA2-65E**	10, 13	25 (11.4)
80E	**145DBA2-80E**	10, 13	25 (11.4)
100E	**145DBA2-100E**	10, 13	25 (11.4)
125E	**145DBA2-125E**	10, 13	25 (11.4)
150E	**145DBA2-150E**	10, 13	25 (11.4)
200E	**145DBA2-200E**	10, 13	25 (11.4)

Contents

Description	*Page*
Product Selection	**V4-T3-117**
Type CLE	**V4-T3-117**
Type HLE	**V4-T3-121**
Type BHLE	**V4-T3-124**
Type HCL	**V4-T3-127**
Type CLS	**V4-T3-129**
Type CLPT	**V4-T3-135**
Type CX	**V4-T3-140**
Type CXN	**V4-T3-144**
Type CXF	**V4-T3-146**
Type DSL	**V4-T3-147**

3

Catalog Number Selection

Easy to Use, Easy to Order!

Eaton's fuse catalog numbering system makes it easy to order the right fuse. The catalog numbers are easy to remember, unique to each fuse, and are broken down in three descriptive segments: Fuse type, voltage rating and current rating.

These catalog numbers can be entered directly and easily:

- No change in order processing will occur if you use either a style number or its corresponding catalog number. You will get the same fuse

Examples:

5CLE-30E—5.5 max. kV, CLE fuse unit, 30E amperes

15CXN-45C—15.5 max. kV, CXN fuse unit, 45C amperes

5CLS-GDM-E—5.5 max. kV, CLS fuse unit, glass polyester nondisconnect mounting

CLE-DL-D—CLE, disconnect live parts Size D

Current Limiting Fuses

15 CLE – 100 E – D

Maximum kV	
2	= 2.4, 2.5, 2.75
4	= 4.3, 4.8
5	= 5.08, 5.5
7	= 7.2
8	= 8.3
15	= 15.5
25	= 25.5
38	= 38.0

Type	
CLE	**CLS75**
HLE	**CX**
BHLE	**CXN**
CLPT	**AHLE**
NCLPT	**ACLS**
CLS	**CXI**
BCLS	**NCLS**
CLS70	

Ampere Rating
0.5 to **1350**

Class
E
R
C
X

Size
A
B
D

Current Limiting Fuse Accessories

15 CLE – P NM – C

Maximum kV
2 = 2.4, 2.5, 2.75
4 = 4.3, 4.8
5 = 5.08, 5.5
7 = 7.2
8 = 8.3
15 = 15.5
25 = 25.5
38 = 38.0

Type	
CLE	**CLS**
HLE	**CLS75**
CLPT	**CX**
NCLPT	**CXN**

Insulator
G = Glass polyester
P = Porcelain
H = High BIL

Hardware
DM = Disconnect mounting
NM = Nondisconnect mounting
DL = Disconnect live parts
NL = Nondisconnect live parts
DF = Disconnect end fittings

Diameter Size
A = 1-5/8 inches (41.3 mm) 0.53E–1.5E single barrel
B = 1-5/8 inches (41.3 mm) 3E–10E single barrel
C = 2-inch (50.8 mm) single barrel
D = 3-inch (76.2 mm) single barrel
E = 3-inch (76.2 mm) double barrel
F = 4-inch (101.6 mm) double barrel
G = 5/8-inch (15.9 mm) ferrule (CX/CXN only)

Product Selection

Type CLE

Type CLE Current Limiting Fuses 2.75 kV Maximum (2.4 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Heritage Product	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Peak Let-Through Current	Catalog Number
15E	1	50	H	Indoor	56353202	56353302	63931702	**2CLE-15E**
20E	1	50	H	Indoor	56353202	56353302	63931702	**2CLE-20E**
25E	1	50	H	Indoor	56353202	56353302	63931702	**2CLE-25E**
10E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-10E**
30E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-30E**
40E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-40E**
50E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-50E**
65E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-65E**
80E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-80E**
100E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-100E**
125E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-125E**
150E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-150E**
200E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-200E**
225E	1	50	H	Indoor	53686104	53686204	63931704	**2CLE-225E**
250E	2	50	H	Indoor	53690002	53690102	63931802	**2CLE-250E**
300E	2	50	H	Indoor	53690002	53690102	63931802	**2CLE-300E**
350X	2	50	H	Indoor	53690002	53690102	63931802	**2CLE-350X**
400X	2	50	H	Indoor	53690002	53690102	63931802	**2CLE-400X**
450X	2	50	H	Indoor	53690002	53690102	63931802	**2CLE-450X**

Type CLE Mountings and Hardware 2.75 kV Maximum (2.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
15E–25E	Non-disconnect	60	2.00 (50.8)	8.13 (206.5)	9.50 (241.3)	2 (0.91)	**2CLE-PNM-C**	**2CLE-GNM-C**	**CLE-NL-C**	—
	Disconnect	60					**2CLE-PDM-C**	**2CLE-GDM-C**	**CLE-DL-C**	**CLE-DF-C**
10E–250E	Non-disconnect	60	3.00 (76.2)	7.00 (177.8)	10.90 (276.9)	7 (3.18)	**2CLE-PNM-D**	**2CLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	60					**2CLE-PDM-D**	**2CLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
300E–450E	Non-disconnect	60	3.00 (76.2)	7.00 (177.8)	10.90 (276.9)	15 (6.81)	**2CLE-PNM-E**	**2CLE-GNM-E**	**CLE-NL-E**	—
	Disconnect	60					**2CLE-PDM-E**	**2CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type CLE Fuse



CLE kV	"L"	"B" Dia.
15E–25E	9.50 (241.3)	2.00 (50.8)
10E–450E	10.90 (276.9)	3.00 (76.2)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type CLE Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Heritage Product	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Peak Let-Through Current	Catalog Number
15E	1	50	H	Indoor	56353204	56353304	63931702	**5CLE-15E**
20E	1	50	H	Indoor	56353204	56353304	63931702	**5CLE-20E**
25E	1	50	H	Indoor	56353204	56353304	63931702	**5CLE-25E**
10E	1	63	—	Indoor/outdoor	70548501	70548601	70548701	**5CLE-10E-D**
15E	1	63	—	Indoor/outdoor	70548501	70548601	70548701	**5CLE-15E-D**
20E	1	63	—	Indoor/outdoor	70548501	70548601	70548701	**5CLE-20E-D**
25E	1	63	—	Indoor/outdoor	70548501	70548601	70548701	**5CLE-25E-D**
30E	1	63	—	Indoor/outdoor	70548501	70548601	70548701	**5CLE-30E**
40E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-40E**
50E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-50E**
65E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-65E**
80E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-80E**
100E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-100E**
125E	1	50	—	Indoor/outdoor	70545801	70545901	70546701	**5CLE-125E**
150E	1	63	—	Indoor/outdoor	70545801	70545901	70547601	**5CLE-150E**
175E	1	63	—	Indoor/outdoor	70545801	70545901	70547601	**5CLE-175E**
200E	1	63	—	Indoor/outdoor	70545801	70545901	70547601	**5CLE-200E**
250E	1	63	—	Indoor/outdoor	70545801	70545901	70547601	**5CLE-250E**
300E	2	63	—	Indoor/outdoor	70546001	70546101	70547601	**5CLE-300E**
350E	2	63	—	Indoor/outdoor	70546001	70546101	70547601	**5CLE-350E**
400E	2	63	—	Indoor/outdoor	70546001	70546101	70547601	**5CLE-400E**
450E	2	63	—	Indoor/outdoor	70546001	70546101	70547601	**5CLE-450E**
600E	2	40	—	Indoor	62908902	62908903	62908904	**5CLE-600E**
750E	2	40	—	Indoor	62908902	62908903	62908904	**5CLE-750E**
1100E	4	31	—	Indoor	62908902	62908903	62908904	**5CLE-1100E**
1350E	4	31	—	Indoor	62908902	62908903	62908904	**5CLE-1350E**

Type CLE Mountings and Hardware 5.5 kV Maximum (4.8 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
10E-D–25E-D 30E–250E	Non-disconnect	60	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	9 (4.09)	**5CLE-PNM-D**	**5CLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	60					**5CLE-PDM-D**	**5CLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
15E–25E	Non-disconnect	60	2.00 (50.8)	11.50 (292.1)	12.90 (327.7)	3 (1.36)	**5CLE-PNM-C**	**5CLE-GNM-C**	**CLE-NL-C**	—
	Disconnect	60					**5CLE-PDM-C**	**5CLE-GDM-C**	**CLE-DL-C**	**CLE-DF-C**
300E–450E	Non-disconnect	60	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	19 (8.63)	**5CLE-PNM-E**	**5CLE-GNM-E**	**CLE-NL-E**	—
	Disconnect	60					**5CLE-PDM-E**	**5CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**
600E and 750E	Consult factory	60	4.00 (101.6)	N/A	N/A	40 (18.16)	—	—	—	—
1100E and 1350E	Consult factory	—	4.00 (101.6)	N/A	N/A	80 (36.32)	—	—	—	—

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type CLE Fuse



CLE kV	"L"	"B" Dia.
15E–25E	12.90 (327.7)	2.00 (50.8)
10E–450E	17.90 (454.7)	3.00 (76.2)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type CLE Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Heritage Product	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Performance Curves Peak Let-Through Current	Catalog Number
15E	1	50	H	Indoor	56353204	56353304	63931703	**8CLE-15E**
20E	1	50	H	Indoor	56353204	56353304	63931703	**8CLE-20E**
25E	1	50	H	Indoor	56353204	56353304	63931703	**8CLE-25E**
10E	1	50	—	Indoor/outdoor	70548501	70548601	70548801	**8CLE-10E-D**
15E	1	50	—	Indoor/outdoor	70548501	70548601	70548801	**8CLE-15E-D**
20E	1	50	—	Indoor/outdoor	70548501	70548601	70548801	**8CLE-20E-D**
25E	1	50	—	Indoor/outdoor	70548501	70548601	70548801	**8CLE-25E-D**
30E	1	50	—	Indoor/outdoor	70548501	70548601	70548801	**8CLE-30E**
40E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-40E**
50E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-50E**
65E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-65E**
80E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-80E**
100E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-100E**
125E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-125E**
150E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-150E**
175E	1	50	—	Indoor/outdoor	70546201	70546301	70547301	**8CLE-175E**
200E	2	50	—	Indoor/outdoor	70546401	70546501	70547301	**8CLE-200E**
250E	2	50	—	Indoor/outdoor	70546401	70546501	70547301	**8CLE-250E**
300E	2	50	—	Indoor/outdoor	70546401	70546501	70547301	**8CLE-300E**
350E	2	50	—	Indoor/outdoor	70546401	70546501	70547301	**8CLE-350E**

Type CLE Mountings and Hardware 8.3 kV Maximum (7.2 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
15E–25E	Non-disconnect	75	2.00 (50.8)	14.00 (355.6)	15.50 (393.7)	3 (1.36)	**8CLE-PNM-C**	**8CLE-GNM-C**	**CLE-NL-C**	—
	Disconnect	75					**8CLE-PDM-C**	**8CLE-GDM-C**	**CLE-DL-C**	**CLE-DF-C**
10E-D–25E-D 30E–175E	Non-disconnect	75	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	9 (4.09)	**8CLE-PNM-D**	**8CLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	75					**8CLE-PDM-D**	**8CLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
200E–350E	Non-disconnect	75	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	19 (8.63)	**8CLE-PNM-E**	**8CLE-GNM-E**	**CLE-NL-E**	—
	Disconnect	75					**8CLE-PDM-E**	**8CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type CLE Fuse



CLE kV	"L"	"B" Dia.
15E–25E	15.50 (393.7)	2.00 (50.8)
10E–350E	17.90 (454.7)	3.00 (76.2)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type CLE Current Limiting Fuses 15.5 kV Maximum (4.8 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Heritage Product	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Peak Let-Through Current	Catalog Number
15E	1	31.5	H	Indoor	56353204	56353304	63931703	**15CLE-15E**
20E	1	31.5	H	Indoor	56353204	56353304	63931703	**15CLE-20E**
25E	1	31.5	H	Indoor	56353204	56353304	63931703	**15CLE-25E**
10E	1	63	—	Indoor/outdoor	70548501	70548601	70548802	**15CLE-10E-D**
15E	1	63	—	Indoor/outdoor	70548501	70548601	70548802	**15CLE-15E-D**
20E	1	63	—	Indoor/outdoor	70548501	70548601	70548802	**15CLE-20E-D**
25E	1	63	—	Indoor/outdoor	70548501	70548601	70548802	**15CLE-25E-D**
30E	1	63	—	Indoor/outdoor	70548501	70548601	70548802	**15CLE-30E**
40E	1	63	—	Indoor/outdoor	70546801	70546901	70547501	**15CLE-40E**
50E	1	63	—	Indoor/outdoor	70546801	70546901	70547501	**15CLE-50E**
65E	1	63	—	Indoor/outdoor	70546801	70546901	70547501	**15CLE-65E**
80E	1	63	②	Indoor/outdoor	70546801	70546901	70547501	**15CLE-80E**
100E	1	63	②	Indoor/outdoor	70546801	70546901	70547501	**15CLE-100E**
125E	1	63	②	Indoor/outdoor	70546801	70546901	70547501	**15CLE-125E**
150E	1	63	②	Indoor/outdoor	70546801	70546901	70547501	**15CLE-150E**
175E	2	63	②	Indoor/outdoor	70547001	70547101	70547501	**15CLE-175E**
200E	2	63	②	Indoor/outdoor	70547001	70547101	70547501	**15CLE-200E**
250E	2	63	②	Indoor/outdoor	70547001	70547101	70547501	**15CLE-250E**
300E	2	63	②	Indoor/outdoor	70547001	70547101	70547501	**15CLE-300E**
80E	2	85	H ②	Indoor	59878302	59878402	63931604	**15CLE2-80E**
100E	2	85	H ②	Indoor	59878302	59878402	63931604	**15CLE2-100E**
125X	2	85	H ②	Indoor	59878302	59878402	63931604	**15CLE2-125X**
150E	3	50	H ②	Indoor	59878302	59878402	63931604	**15CLE3-150E**
175E/200X	3	50	H ②	Indoor	59878302	59878402	63931604	**15CLE3-175E/200X**

Type CLE Mountings and Hardware 15.5 kV Maximum (4.8 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
15E–25E	Non-disconnect	95	2.00 (50.8)	20.00 (508.0)	21.50 (546.1)	4.5 (2.04)	**15CLE-PNM-C**	**15CLE-GNM-C**	**CLE-NL-D**	—
		110					**15CLE-HPNM-C**	—	—	—
	Disconnect	95					**15CLE-PDM-C**	**15CLE-GDM-C**	**CLE-DL-C**	**CLE-DF-C**
		110					**15CLE-HPDM-C**	—	—	—
10E-D–25E-D 30E–150E	Non-disconnect	95	3.00 (76.2)	20.00 (508.0)	23.90 (607.1)	11 (4.99)	**15CLE-PNM-D**	**15CLE-GNM-D**	**CLE-NL-D**	—
		110					**15CLE-HPM-D**	—	—	—
	Disconnect	95					**15CLE-PDM-D**	**15CLE-GNM-D**	**CLE-DL-D**	**CLE-DF-D**
		110					**15CLE-HPDM-D**	—	—	—
175E–300E	Non-disconnect	110	3.00 (76.2)	20.00 (508.0)	23.90 (607.1)	23 (10.44)	**15CLE-PNM-E**	—	**CLE-DL-E**	**CLE-DF-E**
	Disconnect	110					**15CLE-PDM-E**	—	—	—

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type CLE Fuse



CLE kV	"L"	"B" Dia.
15E–25E	21.50 (546.1)	2.00 (50.8)
10E–300E	23.90 (607.1)	3.00 (76.2)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.
② For mountings, consult factory.
③ End fittings supplied only when required.

Type HLE

Type HLE Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal) Interrupting Rating 63 (kA rms Sym.)

Current Rating (Amperes)	Barrel Number	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number	Bolt-In Ferrule Catalog Number	AMPGARD Catalog Number
10E	1	Indoor/outdoor	70548507	70548607	70548703	**5HLE-10E**	**5BHLE-10E**	**5AHLE-10E**
15E	1	Indoor/outdoor	70548507	70548607	70548703	**5HLE-15E**	**5BHLE-15E**	**5AHLE-15E**
20E	1	Indoor/outdoor	70548507	70548607	70548703	**5HLE-20E**	**5BHLE-20E**	**5AHLE-20E**
25E	1	Indoor/outdoor	70548507	70548607	70548703	**5HLE-25E**	**5BHLE-25E**	**5AHLE-25E**
30E	1	Indoor/outdoor	70548507	70548607	70548703	**5HLE-30E**	**5BHLE-30E**	**5AHLE-30E**
40E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-40E**	**5BHLE-40E**	**5AHLE-40E**
50E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-50E**	**5BHLE-50E**	**5AHLE-50E**
65E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-65E**	**5BHLE-65E**	**5AHLE-65E**
80E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-80E**	**5BHLE-80E**	**5AHLE-80E**
100E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-100E**	**5BHLE-100E**	**5AHLE-100E**
125E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-125E**	**5BHLE-125E**	**5AHLE-125E**
150E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-150E**	**5BHLE-150E**	**5AHLE-150E**
175E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-175E**	**5BHLE-175E**	**5AHLE-175E**
200E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-200E**	**5BHLE-200E**	**5AHLE-200E**
250E	1	Indoor/outdoor	70545805	70545905	70547603	**5HLE-250E**	**5BHLE-250E**	**5AHLE-250E**
300E	2	Indoor/outdoor	70546005	70546105	70547603	**5HLE-300E**	**5BHLE-300E**	**5AHLE-300E**
350E	2	Indoor/outdoor	70546005	70546105	70547603	**5HLE-350E**	**5BHLE-350E**	**5AHLE-350E**
400E	2	Indoor/outdoor	70546005	70546105	70547603	**5HLE-400E**	**5BHLE-400E**	**5AHLE-400E**
450E	2	Indoor/outdoor	70546005	70546105	70547603	**5HLE-450E**	**5BHLE-450E**	**5AHLE-450E**

Type HLE Mountings and Hardware 5.5 kV Maximum (4.8 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
10E–250E	Non-disconnect	60	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	**5HLE-PNM-D**	**5HLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	60					**5HLE-PDM-D**	**5HLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
300E–450E	Non-disconnect	60	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	17 (7.72)	**5HLE-PNM-E**	**5HLE-GNM-E**	**CLE-NL-E**	—
	Disconnect	60					**5HLE-PDM-E**	**5HLE-GDM-E**	**CLE-DL-E**	**CLE-DF-D**

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type HLE Fuse



HLE kV	L ± 0.03
5.5	15.88 (403.4)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type HLE Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal) Interrupting Rating 50 (kA Sym.)

Current Rating (Amperes)	Barrel Number	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Peak Let-Through Current	Catalog Number	Bolt-In Ferrule Catalog Number	AMPGARD Catalog Number
10E	1	Indoor/outdoor	70548507	70548607	70548804	**8HLE-10E**	**8BHLE-10E**	**8AHLE-10E**
15E	1	Indoor/outdoor	70548507	70548607	70548804	**8HLE-15E**	**8BHLE-15E**	**8AHLE-15E**
20E	1	Indoor/outdoor	70548507	70548607	70548804	**8HLE-20E**	**8BHLE-20E**	**8AHLE-20E**
25E	1	Indoor/outdoor	70548507	70548607	70548804	**8HLE-25E**	**8BHLE-25E**	**8AHLE-25E**
30E	1	Indoor/outdoor	70548507	70548607	70548804	**8HLE-30E**	**8BHLE-30E**	**8AHLE-30E**
40E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-40E**	**8BHLE-40E**	**8AHLE-40E**
50E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-50E**	**8BHLE-50E**	**8AHLE-50E**
65E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-65E**	**8BHLE-65E**	**8AHLE-65E**
80E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-80E**	**8BHLE-80E**	**8AHLE-80E**
100E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-100E**	**8BHLE-100E**	**8AHLE-100E**
125E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-125E**	**8BHLE-125E**	**8AHLE-125E**
150E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-150E**	**8BHLE-150E**	**8AHLE-150E**
175E	1	Indoor/outdoor	70546203	70546303	70547201	**8HLE-175E**	**8BHLE-175E**	**8AHLE-175E**
200E	2	Indoor/outdoor	70546403	70546503	70547201	**8HLE-200E**	**8BHLE-200E**	**8AHLE-200E**
250E	2	Indoor/outdoor	70546403	70546503	70547201	**8HLE-250E**	**8BHLE-250E**	**8AHLE-250E**
300E	2	Indoor/outdoor	70546403	70546503	70547201	**8HLE-300E**	**8BHLE-300E**	**8AHLE-300E**
350E	2	Indoor/outdoor	70546403	70546503	70547201	**8HLE-350E**	**8BHLE-350E**	**8AHLE-350E**

Type HLE Mountings and Hardware 8.3 kV Maximum (7.2 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
10E–175E	Non-disconnect	75	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	**8HLE-PNM-D**	**8HLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	75					**8HLE-PDM-D**	**8HLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
200E–350E	Non-disconnect	75					**8HLE-PNM-E**	**8HLE-GNM-E**	**CLE-NL-E**	—
	Disconnect	75					**8HLE-PDM-E**	**8HLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type HLE Fuse



HLE kV	L ± 0.03
8.3	15.88 (403.4)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type HLE Current Limiting Fuses 15.5 kV Maximum (14.4 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Indoor/ Outdoor	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Performance Curves Peak Let-Through Current	Catalog Number	Bolt-In Ferrule Catalog Number
10E	1	63	Indoor/outdoor	70548507	70548607	70548805	**15HLE-10E**	**15BHLE-10E**
15E	1	63	Indoor/outdoor	70548507	70548607	70548805	**15HLE-15E**	**15BHLE-15E**
20E	1	63	Indoor/outdoor	70548507	70548607	70548805	**15HLE-20E**	**15BHLE-20E**
25E	1	63	Indoor/outdoor	70548507	70548607	70548805	**15HLE-25E**	**15BHLE-25E**
30E	1	63	Indoor/outdoor	70548507	70548607	70548805	**15HLE-30E**	**15BHLE-30E**
40E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-40E**	**15BHLE-40E**
50E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-50E**	**15BHLE-50E**
65E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-65E**	**15BHLE-65E**
80E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-80E**	**15BHLE-80E**
100E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-100E**	**15BHLE-100E**
125E	1	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-125E**	**15BHLE-125E**
150E	2	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-150E**	**15BHLE-150E**
175E	2	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-175E**	**15BHLE-175E**
200E	2	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-200E**	**15BHLE-200E**
250E	2	63	Indoor/outdoor	70546601	70546701	70547401	**15HLE-250E**	**15BHLE-250E**

Type HLE Mountings and Hardware 15.5 kV Maximum (14.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
10E–175E	Non-disconnect	95	3.00 (76.2)	15.00 (381.0)	18.90 (480.1)	10 (4.54)	**15HLE-PNM-D**	**15HLE-GNM-D**	**CLE-NL-D**	—
	Disconnect	95					**15HLE-PDM-D**	**15HLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
150E–250E	Non-disconnect	95	3.00 (76.2)	15.00 (381.0)	18.90 (480.1)	21 (9.53)	**15HLE-PNM-E**	—	**CLE-NL-E**	—
	Disconnect	95					**15HLE-PDM-E**	—	**CLE-DL-E**	**CLE-DF-E**

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type HLE Fuse



HLE kV	L ± 0.03
15.5	18.88 (479.6)

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Type BHLE

Approximate Dimensions in Inches (mm)

Type BHLE Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal), Indoor, Bolt-In

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
10E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548703	**5BHLE-10E**
15E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548703	**5BHLE-15E**
20E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548703	**5BHLE-20E**
25E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548703	**5BHLE-25E**
30E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548703	**5BHLE-30E**
40E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-40E**
50E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-50E**
65E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-65E**
80E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-80E**
100E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-100E**
125E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-125E**
150E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-150E**
175E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-175E**
200E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-200E**
250E	1	63	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70545805	70545905	70547603	**5BHLE-250E**
300E	2	63	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546005	70546105	70547603	**5BHLE-300E**
350E	2	63	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546005	70546105	70547603	**5BHLE-350E**
400E	2	63	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546005	70546105	70547603	**5BHLE-400E**
450E	2	63	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546005	70546105	70547603	**5BHLE-450E**

Fuse Dimensional Details

Type BHLE Fuse



Type 5BHLE and 8BHLE Fuses

Approximate Dimensions in Inches (mm)

Type BHLE Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal), Indoor, Bolt-In

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
10E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548804	**8BHLE-10E**
15E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548804	**8BHLE-15E**
20E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548804	**8BHLE-20E**
25E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548804	**8BHLE-25E**
30E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70548507	70548607	70548804	**8BHLE-30E**
40E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-40E**
50E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-50E**
65E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-65E**
80E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-80E**
100E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-100E**
125E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-125E**
150E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-150E**
175E	1	50	3.00 (76.2)	15.90 (403.9)	8 (3.63)	70546203	70546303	70547201	**8BHLE-175E**
200E	2	50	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546403	70546503	70547201	**8BHLE-200E**
250E	2	50	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546403	70546503	70547201	**8BHLE-250E**
300E	2	50	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546403	70546503	70547201	**8BHLE-300E**
350E	2	50	3.00 (76.2)	15.90 (403.9)	17 (7.72)	70546403	70546503	70547201	**8BHLE-350E**

Fuse Dimensional Details

Type BHLE Fuse



Type 5BHLE and 8BHLE Fuses

Approximate Dimensions in Inches (mm)

Type BHLE Current Limiting Fuses 15.5 kV Maximum (14.4 kV Nominal), Indoor/Outdoor, Bolt-In

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Performance Curves Total Clearing Time	Peak Let-Through Current	Catalog Number
10E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70548507	70548607	70548805	**15BHLE-10E**
15E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70548507	70548607	70548805	**15BHLE-15E**
20E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70548507	70548607	70548805	**15BHLE-20E**
25E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70548507	70548607	70548805	**15BHLE-25E**
30E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70548507	70548607	70548805	**15BHLE-30E**
40E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-40E**
50E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-50E**
65E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-65E**
80E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-80E**
100E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-100E**
125E	1	63	3.00 (76.2)	18.90 (480.1)	10 (4.54)	70546601	70546701	70547401	**15BHLE-125E**
150E	2	63	3.00 (76.2)	18.90 (480.1)	21 (9.53)	70546601	70546701	70547401	**15BHLE-150E**
175E	2	63	3.00 (76.2)	18.90 (480.1)	21 (9.53)	70546601	70546701	70547401	**15BHLE-175E**
200E	2	63	3.00 (76.2)	18.90 (480.1)	21 (9.53)	70546601	70546701	70547401	**15BHLE-200E**
250E	2	63	3.00 (76.2)	18.90 (480.1)	21 (9.53)	70546601	70546701	70547401	**15BHLE-250E**

Fuse Dimensional Details

Type BHLE Fuse



Type 15BHLE Fuses

Type HCL

Type HCL Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal), Indoor

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Approximate Shipping Weight Lbs (kg)	Mounting Type	Live Parts (Includes End Fittings) Catalog Number	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
10E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70548505	70548605	70548702	**5HCL-10E**
15E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70548505	70548605	70548702	**5HCL-15E**
20E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70548505	70548605	70548702	**5HCL-20E**
25E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70548505	70548605	70548702	**5HCL-25E**
30E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70548505	70548605	70548702	**5HCL-30E**
40E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-40E**
50E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-50E**
65E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-65E**
80E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-80E**
100E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-100E**
125E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-125E**
150E	1	63	3.00 (76.2)	Clip-lock	9 (4.09)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-150E**
200E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-200E**
250E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70545803	70545903	70547602	**5HCL-250E**
300E	2	63	3.00 (76.2)	Clip-lock	20 (9.08)	Non-disconnect	**HCL-NL-1**	70546003	70516103	70547602	**5HCL-300E**
400E	2	63	3.00 (76.2)	Clip-lock	20 (9.08)	Non-disconnect	**HCL-NL-1**	70546003	70516103	70547602	**5HCL-400E**
450E	2	63	3.00 (76.2)	Clip-lock	20 (9.08)	Non-disconnect	**HCL-NL-1**	70546003	70516103	70547602	**5HCL-450E**
500E	2	63	3.00 (76.2)	Clip-lock	20 (9.08)	Non-disconnect	**HCL-NL-1**	66703401	66703501	66703701	**5HCL-500E**
600E	2	63	3.00 (76.2)	Clip-lock	20 (9.08)	Non-disconnect	**HCL-NL-1**	66703401	66703501	66703701	**5HCL-600E**
750E	3	63	3.00 (76.2)	Bolt-in	30 (13.62)	—	—	66703401	66703501	66703701	**5HCL-750E**
	3	63	3.00 (76.2)	Bolt-in	30 (13.62)	—	—	66703401	66703501	66703701	**5BHCL-750E**
900E	3	63	3.00 (76.2)	Bolt-in	30 (13.62)	—	—	66703401	66703501	66703701	**5HCL-900E**
	3	63	3.00 (76.2)	Bolt-in	30 (13.62)	—	—	66703401	66703501	66703701	**5BHCL-900E**

Type HCL Current Limiting Fuses (15.5 kV Maximum, 14.4 kV Nominal), Indoor

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Approximate Shipping Weight Lbs (kg)	Mounting Type	Live Parts (Includes End Fittings) Catalog Number	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
10E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70548503	70548603	70548803	**15HCL-10E**
15E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70548503	70548603	70548803	**15HCL-15E**
20E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70548503	70548603	70548803	**15HCL-20E**
25E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70548503	70548603	70548803	**15HCL-25E**
30E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	70548503	70548603	70548803	**15HCL-30E**
40E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-40E**
50E	1	63	3.00 (76.2)	Clip-lock	10 (4.54)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-50E**
65E	1	50	3.00 (76.2)	Clip-lock	12 (5.45)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-65E**
80E	1	50	3.00 (76.2)	Clip-lock	12 (5.45)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-80E**
100E	1	50	3.00 (76.2)	Clip-lock	12 (5.45)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-100E**
125E	1	50	3.00 (76.2)	Clip-lock	12 (5.45)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-125E**
150E	2	50	3.00 (76.2)	Clip-lock	24 (10.90)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-150E**
200E	2	50	3.00 (76.2)	Clip-lock	24 (10.90)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-200E**
250E	2	50	3.00 (76.2)	Clip-lock	24 (10.90)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-250E**
300E	2	50	3.00 (76.2)	Clip-lock	24 (10.90)	Non-disconnect	**HCL-NL-1**	66703201	66703301	70547402	**15HCL-300E**

Note

Approximate Dimensions in Inches (mm).

3

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

5.5 and 15.5 kV Clip Lock Mounted

Ampere Rating	Number of Barrels	Figure Number	A	B	C	Interrupting Rating rms (kA Sym.)
5.5 kV Maximum—Clip Lock Style—15.25-Inch (387.4 mm) Clip Centers—3.00-Inch (76.2 mm) Barrel Diameter						
10E–150E	1	A	16.81 (427.0)	16.12 (409.4)	①	63
5.5 kV Maximum—Clip Lock Style—21.25-Inch (539.8 mm) Clip Centers—3.00-Inch (76.2 mm) Barrel Diameter						
200E–600E	1	A	22.81 (579.4)	22.12 (561.8)	①	63

15.5 kV Clip Lock Mounted

Ampere Rating	Number of Barrels	Figure Number	A	B	C	Interrupting Rating rms (kA Sym.)
15.5 kV Maximum—Clip Lock Style—21.25-Inch (539.8 mm) Clip Centers—3.00-Inch (76.2 mm) Barrel Diameter						
65E–125E	1	A	22.81 (579.4)	22.12 (561.8)	①	63
150E–300E	2	B	22.81 (579.4)	22.12 (561.8)	①	50
15.5 kV Maximum—Clip Lock Style—18.25-Inch (463.6 mm) Clip Centers—3.00-Inch (76.2 mm) Barrel Diameter						
10E–50E	1	A	19.81 (503.2)	19.12 (485.6)	①	63

Bolt-In Series—5.5 kV

Ampere Rating	Number of Barrels	Figure Number	A	B	C	D	Interrupting Rating rms (kA Sym.)
5.5 kV Maximum—Bolt-in Style—23.73-Inch (602.7 mm) Hole Centers—3.00-Inch (76.2 mm) Barrel Diameter							
750E, 900E	3	C	25.11 (637.8)	22.37 (568.2)	23.73 (602.7)	①	63

Type HCL Fuse Dimensional Details

Type HCL-14 Fuses



Figure A



Figure B



Figure C

Type HCL Fuses



Note

① 0.5 (12.7) tripped force 2 lb (0.9 kg).

Type CLS

Type CLS Current Limiting Fuses

Maximum Design Voltage (kV)	Current Rating (Amperes)	"R" Designation	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves			Catalog Number
									Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	
2.54	25	—	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-25**
	70	2R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-2R**
	100	3R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-3R**
	130	4R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-4R**
	150	5R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-5R**
	170	6R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-6R**
	200	9R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-9R**
	230	12R	1	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2CLS-12R**
	390	18R	2	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2CLS-18R**
	450	24R	2	50	3.00 (76.2)	7.00 (177.8)	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2CLS-24R**
	25	—	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-25**
	70	2R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2ACLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2ACLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2ACLS-24R**
	25	—	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-25**
	70	2R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	8 (3.63)	66664702	66664704	66700202	**2BCLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	17 (7.72)	66664702	66664704	66700202	**2BCLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	17 (7.72)	66664702	66664704	66700202	**2BCLS-24R**
	25	—	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-25**
	70	2R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	10.80 (274.3)	7 (3.18)	66664702	66664704	66700202	**2HCLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2HCLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	10.80 (274.3)	16 (7.26)	66664702	66664704	66700202	**2HCLS-24R**

Note

Approximate Dimensions in Inches (mm).

Type CLS Current Limiting Fuses, continued

Maximum Design Voltage (kV)	Current Rating (Amperes)	"R" Designation	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves			Catalog Number
									Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	
5.08	30	—	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-30**
	70	2R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-2R**
	100	3R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-3R**
	130	4R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-4R**
	150	5R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-5R**
	170	6R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-6R**
	200	9R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-9R**
	230	12R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5CLS-12R**
	390	18R	2	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5CLS-18R**
	450	24R	2	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5CLS-24R**
5.08	30	—	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-30**
	70	2R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5ACLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5ACLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5ACLS-24R**
4.3	480	26R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**4ACLS-26R**
5.08	30	—	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-30**
	70	2R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5BCLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5BCLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5BCLS-24R**
4.3	480	26R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**4BCLS-26R**
5.08	30	—	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-30**
	70	2R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-6R**
	200	9R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66690602	66690702	66700203	**5HCLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5HCLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66690602	66690702	66700203	**5HCLS-24R**

Note

Approximate Dimensions in Inches (mm).

Type CLS Current Limiting Fuses, continued

Maximum Design Voltage (kV)	Current Rating (Amperes)	"R" Designation	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves			Catalog Number
									Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	
5.08	70	2R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-2R**
	100	3R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-3R**
	130	4R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-4R**
	150	5R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-5R**
	170	6R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-6R**
	200	9R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66690602	66690702	66700203	**5CLS70-9R**
	230	12R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-12R**
	390	18R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-18R**
	450	24R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-24R**
	600	32R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-32R**
	650	36R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-36R**
	700	44R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66690602	66690702	66700203	**5CLS70-44R**
5.5	70	2R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-2R**
	100	3R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-3R**
	130	4R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-4R**
	150	5R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-5R**
	170	6R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-6R**
	200	9R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-9R**
	230	12R	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	51285302	51285402	66700204	**5LCLS-12R**
	390	18R	2	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	22 (9.99)	51285302	51285402	66700204	**5LCLS-18R**
	450	24R	2	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	22 (9.99)	51285302	51285402	66700204	**5LCLS-24R**
8.3	70	2R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**8CLS-2R**
	100	3R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**8CLS-3R**
	130	4R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**8CLS-4R**
	150	5R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**8CLS-5R**
	170	6R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**8CLS-6R**
7.2	200	9R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**7CLS-9R**
	230	12R	1	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	7 (3.18)	66700602	66700702	66700205	**7CLS-12R**
	390	18R	2	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	16 (7.26)	66700602	66700702	66700205	**7CLS-18R**
	450	24R	2	50	3.00 (76.2)	12.00 (304.8)	15.90 (403.9)	16 (7.26)	66700602	66700702	66700205	**7CLS-24R**
8.3	70	2R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-6R**
7.2	200	9R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	7 (3.18)	66700602	66700702	66740205	**7BCLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	16 (7.26)	66700602	66700702	66740205	**7BCLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	16 (7.26)	66700602	66700702	66740205	**7BCLS-24R**
8.3	70	2R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**8ACLS-2R**
	100	3R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**8ACLS-3R**
	130	4R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**8ACLS-4R**
	150	5R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**8ACLS-5R**
	170	6R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**8ACLS-6R**

Note

Approximate Dimensions in Inches (mm).

Type CLS Current Limiting Fuses, continued

Maximum Design Voltage (kV)	Current Rating (Amperes)	"R" Designation	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves: Minimum Melting Time	Performance Curves: Total Clearing Time	Performance Curves: Peak Let-Through Current	Catalog Number
7.2	200	9R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**7ACLS-9R**
	230	12R	1	50	3.00 (76.2)	Not applicable	15.90 (403.9)	8 (3.63)	66700602	66700702	66740205	**7ACLS-12R**
	390	18R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66700602	66700702	66740205	**7ACLS-18R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	17 (7.72)	66700602	66700702	66740205	**7ACLS-24R**
	450	24R	2	50	3.00 (76.2)	Not applicable	15.90 (403.9)	20 (9.08)	66700602	66700702	66740205	**7CLS70-24R**
	650	36R	3	50	3.00 (76.2)	Not applicable	15.90 (403.9)	30 (13.62)	66700602	66700702	66740205	**7CLS70-36R**
	700	44R	2	50	4.00 (101.6)	Not applicable	15.90 (403.9)	40 (18.16)	66700602	66700702	66740205	**7CLS70-44R**
8.3	15	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-15**
	30	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-30**
	60	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-60**
	70	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-70**
	90	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-90**
	110	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-110**
	125	Not applicable	1	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	11 (4.99)	66664202	66664302	66679802	**8CLS-125**
	150	Not applicable	2	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	22 (9.99)	66664202	66664302	66679802	**8CLS-150**
	200	Not applicable	2	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	22 (9.99)	66664202	66664302	66679802	**8CLS-200**
	225	Not applicable	2	50	3.00 (76.2)	14.00 (355.6)	17.90 (454.7)	22 (9.99)	66664202	66664302	66679802	**8CLS-225**

Note

Approximate Dimensions in Inches (mm).

Fuse Dimensional Details

Approximate Dimensions in Inches (mm)

Type CLS Fuse



Type BCLS Fuse



Type 5BCLS and 7BCLS Fuses



Type 2BCLS Fuse

Type CLS Mountings and Hardware

Maximum Design Voltage (kV)	Ampere Rating	Fuse Mounting Type	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ① Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ① Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) Catalog Number	End Fittings (Disconnect Only) ① Catalog Number
2.54	25–230	Non-disconnect	60	**2CLE-PNM-D**	**2CLE-GNM-D**	**CLE-NL-D**	—
		Disconnect	60	**2CLE-PDM-D**	**2CLE-GDM-E**	**CLE-DL-D**	**CLE-DF-D**
	390–450	Non-disconnect	60	**2CLE-PNM-E**	**2CLE-GNM-E**	**CLE-NL-E**	—
		Disconnect	60	**2CLE-PDM-E**	**2CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**
5.5 (CLS)	30–230	Non-disconnect	60	**5HLE-PNM-D**	**5HLE-GNM-D**	**CLE-NL-D**	—
		Disconnect	60	**5HLE-PDM-D**	**5HLE-GDM-E**	**CLE-DL-D**	**CLE-DF-D**
	390–480	Non-disconnect	60	**5HLE-PNM-E**	**5HLE-GNM-E**	**CLE-NL-E**	—
		Disconnect	60	**5HLE-PDM-E**	**5HLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**
5.5 (LCLS)	70–230	Non-disconnect	60	**5CLE-PNM-D**	**5CLE-GNM-D**	**CLE-NL-D**	—
		Disconnect	60	**5CLE-PDM-D**	**5CLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
			75	**8CLE-PDM-D**	**8CLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
	390–450	Non-disconnect	60	**5CLE-PNM-E**	**5CLE-GNM-E**	**CLE-NL-E**	—
		Disconnect	60	**5CLE-PDM-E**	**5CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**
			75	**8CLE-PDM-E**	**8CLE-PDM-E**	**CLE-DL-E**	**CLE-DF-E**
8.3	70–100	Non-disconnect	75	**8HLE-PNM-D**	**8HLE-GNM-D**	**CLE-NL-D**	—
	130–230	Disconnect	75	**8HLE-PDM-D**	**8HLE-GDM-D**	**CLE-DL-D**	**CLE-DF-D**
7.2	390–450	Non-disconnect	75	**8HLE-PDM-E**	**8HLE-GNM-E**	**CLE-NL-E**	—
		Disconnect	75	**8HLE-PDM-E**	**8HLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**
8.3	15–30	Non-disconnect	75	**8CLE-PNM-D**	**8CLE-GNM-D**	**CLE-NL-D**	—
	60–125	Disconnect	75	**8CLE-PDM-D**	**8CLE-GDM-D**	**CLE-DL-D**	**CLS-DF-D**
	150–225	Non-disconnect	75	**8CLE-PNM-E**	**8CLE-GNM-E**	**CLE-NL-E**	—
		Disconnect	75	**8CLE-PDM-E**	**8CLE-GDM-E**	**CLE-DL-E**	**CLE-DF-E**

Note

① Disconnect only.

Type CLPT

Indicating

Type CLPT Current Limiting Fuses 2.475 kV Maximum (2.4 kV Nominal)

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves		Peak Let-Through Current	Catalog Number
						Minimum Melting Time	Total Clearing Time		
0.25E	63	0.81 (20.6)	—	4.50 (114.3)	0.25 (0.11)	56357202	59883702	63933702	**2NCLPT-.25E**
0.5E	63	0.81 (20.6)	—	4.50 (114.3)	0.25 (0.11)	56357202	59883702	63933702	**2NCLPT-.5E**
1E	40	0.81 (20.6)	—	4.50 (114.3)	0.25 (0.11)	56357202	59883702	63933702	**2NCLPT-1E**
2E	40	0.81 (20.6)	—	4.50 (114.3)	0.25 (0.11)	56357202	59883702	63933702	**2NCLPT-2E**
5E	25	0.81 (20.6)	—	4.50 (114.3)	0.25 (0.11)	56357202	59883702	63933702	**2NCLPT-5E**

Note

Approximate Dimensions in Inches (mm).

Type CLPT Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal)

Non-Indicating

Indicating

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves: Minimum Melting Time	Performance Curves: Total Clearing Time	Performance Curves: Peak Let-Through Current	Catalog Number
Non-Indicating									
0.5E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-.5E**
1E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-1E**
2E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-2E**
3E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-3E**
4E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-4E**
5E	63	0.81 (20.6)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**5NCLPT-5E**
0.5E	50	1.00 (25.4)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**317B487H02**
1E	50	1.00 (25.4)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**317B487H06**
2E	50	1.00 (25.4)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**317B487H03**
3E	50	1.00 (25.4)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**317B487H04**
5E	50	1.00 (25.4)	—	5.63 (143.0)	0.25 (0.11)	66702402	66702502	66704101	**317B487H05**
0.5E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-.5E-A**
1E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-1E-A**
2E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-2E-A**
3E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-3E-A**
5E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-5E-A**
10E	63	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	70548302	70548402	63934002	**5NCLPT-10E-A**
Indicating									
0.5E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-.5E**
1E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-1E**
1.5E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-1.5E**
3E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-3E**
5E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-5E**
10E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.2 (0.54)	56353206	56353306	63934001	**5CLPT-10E**

Type CLPT Mountings and Hardware 5.5 kV Maximum (4.8 kV Nominal) ③

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ②: Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ②: Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
0.5–2	Non-disconnect	60	**5CLPT-PNM-A**	**5CLPT-GNM-A**	**CLPT-NL**	—
	Disconnect	60	**5CLPT-PDM-A**	**5CLPT-GDM-A**	**CLPT-DL**	**CLPT-DF**
3–10	Non-disconnect	60	**5CLPT-PNM-B**	**5CLPT-GNM-B**	**CLPT-NL**	—
	Disconnect	60	**5CLPT-PDM-B**	**5CLPT-GDM-B**	**CLPT-DL**	**CLPT-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

③ Refers only to 5CLPT and 5NCLPT-A fuses only.

Approximate Dimensions in Inches (mm).

Type CLPT Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal)

Non-Indicating

Indicating

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves: Minimum Melting Time	Performance Curves: Total Clearing Time	Performance Curves: Peak Let-Through Current	Catalog Number
Non-Indicating									
2E	25	0.81 (20.6)	—	8.00 (203.2)	0.25 (0.11)	56357206	59883706	63933704	**8NCLPT-2E**
4E	25	0.81 (20.6)	—	8.00 (203.2)	0.25 (0.11)	56357206	59883706	63933704	**8NCLPT-4E**
10E	50	1.10 (27.9)	—	5.00 (127.0)	0.5 (0.23)	56357206	59883706	63933704	**8NCLPT-0E**
1E	50	1.10 (27.9)	—	5.00 (127.0)	0.5 (0.23)	56357206	59883706	63933704	**8NCLPT-1E**
5E	50	1.10 (27.9)	—	5.00 (127.0)	0.5 (0.23)	56357206	59883706	63933704	**8NCLPT-5E**
0.5E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.5 (0.70)	70548303	70548403	63934002	**8NCLPT-.5E-A**
1E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.5 (0.70)	70548303	70548403	63934002	**8NCLPT-1E-A**
2E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.5 (0.70)	70548303	70548403	63934002	**8NCLPT-2E-A**
3E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.5 (0.70)	70548303	70548403	63934002	**8NCLPT-3E-B**
5E	50	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	70548303	70548403	63934002	**8NCLPT-5E-B**
10E	50	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	70548303	70548403	63934002	**8NCLPT-10E-B**
Indicating									
.5E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.5 (0.70)	56353206	56353306	63934001	**8CLPT-.5E**
3E	80	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.6 (0.73)	56353206	56353306	63934001	**8CLPT-3E**
5E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.6 (0.73)	56353206	56353306	63934001	**8CLPT-5E**
10E	50	1.60 (40.6)	8.10 (205.7)	9.50 (241.3)	1.6 (0.73)	56353206	56353306	63934001	**8CLPT-10E**

Type CLPT Mountings and Hardware 8.3 kV Maximum (7.2 kV Nominal) ③

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ②: Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ②: Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ②: Catalog Number	End Fittings (Disconnect Only): Catalog Number
0.5–2	Non-disconnect	75	**8CLPT-PNM-A**	**8CLPT-GNM-A**	**CLPT-NL**	—
	Disconnect	75	**8CLPT-PDM-A**	**8CLPT-GDM-A**	**CLPT-DL**	**CLPT-DF**
3–10	Non-disconnect	75	**8CLPT-PNM-B**	**8CLPT-GNM-B**	**CLPT-NL**	—
	Disconnect	75	**8CLPT-PDM-B**	**8CLPT-GDM-B**	**CLPT-DL**	**CLPT-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.
② End fittings supplied only when required.
③ Refers only to 8CLPT and 8NCLPT-A or -B fuses only.

Approximate Dimensions in Inches (mm).

Type CLPT Current Limiting Fuses 15.5 kV Maximum (7.2 kV Nominal)

Non-Indicating

Indicating

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves: Minimum Melting Time	Performance Curves: Total Clearing Time	Performance Curves: Peak Let-Through Current	Catalog Number
Non-Indicating									
0.5E	63	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	70548303	70548403	63934002	**15NCLPT-.5E**
1E	63	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	70548303	70548403	63934002	**15NCLPT-1E**
2E	63	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	70548303	70548403	63934002	**15NCLPT-1.5E**
3E	63	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	70548303	70548403	63934002	**15NCLPT-3E**
5E	63	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	70548303	70548403	63934002	**15NCLPT-5E**
10E	63	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	70548303	70548403	63934002	**15NCLPT-10E**
Indicating									
0.5E	80	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	56353206	56353306	63934001	**15CLPT-.5E**
1E	80	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	56353206	56353306	63934001	**15CLPT-1E**
2E	80	1.60 (40.6)	11.50 (292.1)	12.90 (327.7)	1.6 (0.73)	56353206	56353306	63934001	**15CLPT-1.5E**
3E	80	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	56353206	56353306	63934001	**15CLPT-3E**
5E	80	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	56353206	56353306	63934001	**15CLPT-5E**
10E	50	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	56353206	56353306	63934001	**15CLPT-10E**

Type CLPT Mountings and Hardware 15.5 kV Maximum (14.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ②: Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ②: Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ②: Catalog Number	End Fittings (Disconnect Only): Catalog Number
0.5–2	Non-disconnect	95	**15CLPT-PNM-A**	**15CLPT-GNM-A**	**CLPT-NL**	—
	Disconnect	95	**15CLPT-PDM-A**	**15CLPT-GDM-A**	**CLPT-DL**	**CLPT-DF**
3–10	Non-disconnect	95	**15CLPT-PNM-B**	**15CLPT-GNM-B**	**CLPT-NL**	**CLPT-DF**
	Disconnect	95	**15CLPT-PDM-B**	**15CLPT-GDM-B**	**CLPT-DL**	—

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CLPT Current Limiting Fuses 25.5 kV Maximum (23.0 kV Nominal)

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
0.5E	44	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	56353208	56353308	63933901	**25CLPT-.5E**
1E	44	1.60 (40.6)	16.10 (408.9)	17.60 (447.0)	2 (0.91)	56353208	56353308	63933901	**25CLPT-1E**

Type CLPT Mountings and Hardware 25.5 kV Maximum (23.0 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
0.5E–1E	Non-disconnect	150	**25CLPT-PNM-A**	—	**25CLPT-NL**	—
	Disconnect	150	**25CLPT-PDM-A**	—	**25CLPT-DL**	**CLPT-DF**

Type CLPT Current Limiting Fuses 38.0 kV Maximum (34.5 kV Nominal)

Current Rating (Amperes)	Interrupting Rating rms (kA Sym.)	Diameter	Clip Center	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	Catalog Number
0.5E	44	1.60 (40.6)	17.10 (434.3)	18.60 (472.4)	2 (0.91)	56353208	56353308	63933901	**38CLPT-.5E**

Type CLPT Mountings and Hardware 38.0 kV Maximum (34.5 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
0.5E	Disconnect	—	Not applicable	Not applicable	**25CLPT-NL**	**CLPT-DF**
	Non-disconnect	—	Not applicable	Not applicable	**25CLPT-DL**	—

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CX

Type CX

Type CX Current Limiting Fuses 4.3 kV Maximum (2.4 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Fuse Mounting Code	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	I^2t	Catalog Number
Non-Indicating											
18C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CX-18C**
25C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CX-25C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CX-35C**
45C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544101	TC70544501	TC70544901	TC70545101	**4CX-45C**
50C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544101	TC70544501	TC70544901	TC70545101	**4CX-50C**
60C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544502	TC70544901	TC70545101	**4CX-60C**
65C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CX-65C**
75C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CX-75C**
80C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544502	TC70544901	TC70545101	**4CX-80C**
100C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CX-100C**
Indicating											
18C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CXI-18C**
25C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CXI-25C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	1 (0.45)	TC70544101	TC70544501	TC70544901	TC70545101	**4CXI-35C**
45C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544101	TC70544501	TC70544901	TC70545101	**4CXI-45C**
50C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544101	TC70544501	TC70544901	TC70545101	**4CXI-50C**
60C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544502	TC70544901	TC70545101	**4CXI-60C**
65C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CXI-65C**
75C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CXI-75C**
80C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544502	TC70544901	TC70545101	**4CXI-80C**
100C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544102	TC70544501	TC70544901	TC70545101	**4CXI-100C**

Type CX Mountings and Hardware 4.3 kV Maximum (2.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Size	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
18C–100C	Non-disconnect	A	60	—	**5CX-GNM-G**	**CX-NL**	—
	Disconnect	A	60	—	**5CX-GDM-G**	**CX-DL**	**CX-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CX

Type CX Current Limiting Fuses 5.5 kV Maximum (4.8 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Fuse Mounting Code	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	I^2t	Catalog Number
Non-Indicating											
10C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-10C**
12C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-12C**
18C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-18C**
20C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-20C**
21C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CX-21C**
25C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-25C**
30C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-30C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CX-35C**
40C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-40C**
50C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-50C**
60C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CX-60C**
65C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-65C**
75C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CX-75C**
Indicating											
10C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-10C**
12C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-12C**
18C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-18C**
20C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-20C**
21C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CXI-21C**
25C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-25C**
30C	1	50	G	1.13 (28.7)	10.00 (254.0)	1 (0.45)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-30C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CXI-35C**
40C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-40C**
50C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-50C**
60C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544202	TC70544602	TC70544902	TC70545201	**5CXI-60C**
65C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-65C**
75C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544201	TC70544601	TC70544902	TC70545201	**5CXI-75C**

Type CX Mountings and Hardware 5.5 kV Maximum (4.8 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Size	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
10C–75C	Non-disconnect	A	60	—	**5CX-GNM-G**	**CX-NL**	—
	Disconnect	A	60	—	**5CX-GDM-G**	**CX-DL**	**CX-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CX

Type CX Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Fuse Mounting Code	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	I^2t	Catalog Number
Non-Indicating											
3.5C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CX-3.5C**
4C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CX-4C**
4.5C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-4.5C**
6C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-6C**
7C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CX-7C**
8C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-8C**
10C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-10C**
12C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-12C**
15C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CX-15C**
18C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-18C**
20C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-20C**
25C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-25C**
30C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-30C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CX-35C**
40C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CX-40C**
Indicating											
3.5C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CXI-3.5C**
4C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CXI-4C**
4.5C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-4.5C**
6C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-6C**
7C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CXI-7C**
8C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-8C**
10C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-10C**
12C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-12C**
15C	1	50	G	1.13 (28.7)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CXI-15C**
18C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-18C**
20C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-20C**
25C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-25C**
30C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-30C**
35C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544302	TC70544702	TC70545001	TC70545301	**8CXI-35C**
40C	1	50	G	2.00 (50.8)	10.00 (254.0)	2 (0.91)	TC70544301	TC70544701	TC70545001	TC70545301	**8CXI-40C**

Type CX Mountings and Hardware 8.3 kV Maximum (7.2 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Size	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
3.5C–40C	Non-disconnect	B	75	—	**8CX-GNM-G**	**CX-NL**	—
	Disconnect	B	75	—	**8CX-GDM-G**	**CX-DL**	**CX-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CX

Type CX Current Limiting Fuses 15.5 kV Maximum (14.4 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Fuse Mounting Code	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current	I^2t	Catalog Number
Non-Indicating											
4C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-4C**
6C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-6C**
7C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544402	TC70544802	TC70545002	TC70545401	**15CX-7C**
8C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-8C**
10C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-10C**
12C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-12C**
15C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544402	TC70544802	TC70545002	TC70545401	**15CX-15C**
18C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-18C**
20C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-20C**
25C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-25C**
30C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-30C**
40C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CX-40C**
Indicating											
4C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-4C**
6C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-6C**
7C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544402	TC70544802	TC70545002	TC70545401	**15CXI-7C**
8C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-8C**
10C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-10C**
12C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-12C**
15C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544402	TC70544802	TC70545002	TC70545401	**15CXI-15C**
18C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-18C**
20C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-20C**
25C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-25C**
30C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-30C**
40C	1	50	G	2.00 (50.8)	14.30 (363.2)	2 (0.91)	TC70544401	TC70544801	TC70545002	TC70545401	**15CXI-40C**

Type CX Mountings and Hardware 15.5 kV Maximum (14.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Size	Voltage BIL (kV)	Mounting (Including Live Parts, End Fittings) ② Porcelain Insulator Catalog Number	Mounting (Including Live Parts, End Fittings) ② Glass-Polyester Insulator Catalog Number	Live Parts (Including End Fittings) ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
4C–40C	Non-disconnect	C	95	—	**15CX-GNM-G**	**CX-NL**	—
	Disconnect	C	95	—	**15CX-GDM-G**	**CX-DL**	**CX-DF**

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CXN

Type CXN Current Limiting Fuses 8.3 kV Maximum (7.2 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current		Catalog Number
60C	1	50	3.00 (76.2)	18.80 (477.5)	8 (3.63)	66675102	66675202	66664902		**8CXN-60C**
100C	1	50	3.00 (76.2)	18.80 (477.5)	8 (3.63)	66675102	66675202	66664902		**8CXN-100C**
125C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66675102	66675202	66664902		**8CXN-125C**
150C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66675102	66675202	66664902		**8CXN-150C**
200C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66675102	66675202	66664902		**8CXN-200C**
250C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66675102	66675202	66664902		**8CXN-250C**
120C	2	50	3.00 (76.2)	18.80 (477.5)	16 (7.26)	66675104	66675204	66664902	2 X 60C	**8CXN-120C**
200C	2	50	3.00 (76.2)	18.80 (477.5)	16 (7.26)	66675104	66675204	66664902	2 X 100C	**8CXN-200C**
250C	2	50	3.00 (76.2)	18.80 (477.5)	16 (7.26)	66675104	66675204	66664902	2 X 125C	**8CXN-250C**
300C	2	50	4.00 (101.6)	18.80 (477.5)	28 (12.71)	66675104	66675204	66664902	2 X 150C	**8CXN-300C**

Type CXN Mountings and Hardware 8.3 kV Maximum (7.2 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage LIWL (BIL)	Glass Polyester Insulator Mounting (Including Live Parts, End Fittings) ② Catalog Number	Live Parts ② Catalog Number	End Fittings (Disconnect Only) Catalog Number
60C–100C Single barrel	Non-disconnect	95	**15CXN-GNM-D**	**15CXN-NL-D**	—
	Non-disconnect	95	**15CXN-GNM-G**	**15CXN-NL-G**	—
	Disconnect	95	**15CXN-GDM-G**	**15CXN-DL-G**	**15CXN-DF-G**
125C–250C Single barrel	Non-disconnect	95	**15CXN-GNM-F**	**15CXN-NL-F**	—
	Non-disconnect	95	**15CXN-GNM-G**	**15CXN-NL-G**	—
	Disconnect	95	**25CXN-GDM-G**	**15CXN-DL-G**	**15CXN-DF-G**
120C, 200C Double barrel	Non-disconnect	95	**15CXN-GNM-D**	**15CXN-NL-D**	—
250C, 300C Double barrel	Non-disconnect	95	**15CXN-GNM-F**	**15CXN-NL-F**	—

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CXN

Type CXN Current Limiting Fuses 15.5 kV Maximum (14.4 kV Nominal)

Current Rating (Amperes)	Barrel Number	Interrupting Rating rms (kA Sym.)	Diameter	Length	Approximate Shipping Weight Lbs (kg)	Performance Curves Minimum Melting Time	Total Clearing Time	Peak Let-Through Current		Catalog Number
45C	1	50	3.00 (76.2)	18.80 (477.5)	8 (3.63)	66674802	66675002	66665002		**15CXN-45C**
60C	1	50	3.00 (76.2)	18.80 (477.5)	8 (3.63)	66674802	66675002	66665002		**15CXN-60C**
75C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66674802	66675002	66665002		**15CXN-75C**
85C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66674802	66675002	66665002		**15CXN-85C**
100C	1	50	4.00 (101.6)	18.80 (477.5)	14 (6.36)	66674802	66675002	66665002		**15CXN-100C**
90C	2	50	3.00 (76.2)	18.80 (477.5)	16 (7.26)	66674804	66675004	66665002	2 X 45C	**15CXN-90C**
120C	2	50	3.00 (76.2)	18.80 (477.5)	16 (7.26)	66674804	66675004	66665002	2 X 60C	**15CXN-120C**
150C	2	50	4.00 (101.6)	18.80 (477.5)	28 (12.71)	66674804	66675004	66665002	2 X 75C	**15CXN-150C**
175C	2	50	4.00 (101.6)	18.80 (477.5)	28 (12.71)	66674804	66675004	66665002	2 X 85C	**15CXN-175C**

Type CXN Mountings and Hardware 15.5 kV Maximum (14.4 kV Nominal)

Ampere Rating	Fuse Mounting Type ①	Voltage LIWL (BIL)	Glass Polyester Insulator Mounting (Including Live Parts, End Fittings) ② Catalog Number	Live Parts ② Catalog Number	End Fittings (Disconnect Only Catalog Number
45C–60C Single barrel	Non-disconnect	95	**15CXN-GNM-D**	**15CXN-NL-D**	—
	Non-disconnect	95	**15CXN-GNM-G**	**15CXN-NL-G**	—
	Disconnect	95	**15CXN-GDM-G**	**15CXN-DL-G**	**15CXN-DF-G**
75C–100C Single barrel	Non-disconnect	95	**15CXN-GNM-F**	**15CXN-NL-F**	—
	Non-disconnect	95	**15CXN-GNM-G**	**15CXN-NL-G**	—
	Disconnect	95	**25CXN-GDM-G**	**15CXN-DL-G**	**15CXN-DF-G**
90C, 120C Double barrel	Non-disconnect	95	**15CXN-GNM-D**	**15CXN-NL-D**	—
150C, 175C Double barrel	Non-disconnect	95	**15CXN-GNM-F**	**15CXN-NL-F**	—

Notes

① See **Page V4-T3-148** for diagram of typical mounting.

② End fittings supplied only when required.

Approximate Dimensions in Inches (mm).

Type CXF

Type CXF Indicated Full-Range Current-Limiting Fuses Mountings and Hardware

Maximum Design Voltage (kV)	Ampere Rating	Mounting Fuse Mounting Type	Voltage BIL (kV)	Catalog Number	Live Parts Catalog Number	End Fittings Catalog Number
5.5	80–100	Non-disconnect	—	—	**CXN-NL-G**	—
	125–200	Disconnect	—	—	**CXN-GL-G**	**CXN-DF-G**
10	6–18	Non-disconnect	75	**8CX-GNM-G**	**CX-NL**	—
	20–50	Disconnect	75	**8CX-GDM-G**	**CX-DL**	**CX-DF**
8.3	65–80	Non-disconnect	—	—	**CXN-NL-G**	—
	100–125	Disconnect	—	—	**CXN-DL-G**	**CXN-DF-G**
17.2	6–18	Non-disconnect	95	**15CX-GNM-G**	**CX-NL**	—
	20–50	Disconnect	95	**15CX-GDM-G**	**CX-DL**	**CX-DF**
15.5	65–80	Non-disconnect	—	—	**CXN-NL-G**	—
	100	Disconnect	—	—	**CXN-DL-G**	**CXN-DF-G**
23	6–18	Non-disconnect	—	—	**CX-NL**	—
	20–50	Disconnect	—	—	**CX-DL**	**CX-DF**

Type DSL

6DSL-B1600

Type DSL Low Voltage Current Limiting Fuse

Fuse Type/Voltage	Interrupting Rating rms (kA Sym.)	Application Data (Time Current Curves)	Approximate Ship Wt. Lbs (kg)	Catalog Number
Type DSL fuse units 600V nominal	200	33–792 (2)	3.00 (1.4)	**6DSL-A150**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A200**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A250**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A300**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A400**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A600**
	200	33–792 (2)	3.00 (1.4)	**6DSL-A800**
	200	33–792 (2)	4.00 (1.8)	**6DSL-B1200**
	200	33–792 (2)	4.00 (1.8)	**6DSL-B1600**
	200	33–792 (2)	4.00 (1.8)	**6DSL-B2000**
	200	33–792 (3)	5.50 (2.5)	**6DSL-C800**
	200	33–792 (3)	5.50 (2.5)	**6DSL-C1000**
	200	33–792 (3)	5.50 (2.5)	**6DSL-C1200**
	200	33–792 (3)	5.50 (2.5)	**6DSL-C1600**
	200	33–792 (3)	5.50 (2.5)	**6DSL-C2000**
	200	33–792 (3)	8.50 (3.9)	**6DSL-D2500**
	200	33–792 (3)	8.50 (3.9)	**6DSL-D3000**
	200	33–792	20.00 (9.1)	**6DSL-E2500**
	200	33–792	20.00 (9.1)	**6DSL-E3000**
	200	33–792	20.00 (9.1)	**6DSL-E4000**
	200	33–792	24.00 (10.9)	**6DSL-F5000**

Typical Fuse Mounting for Current Limiting Fuses

Single Barrel Disconnect with 2.00-Inch (50.8 mm) Diameter CLE Fuses



Non-Disconnect (CX)



Double-Barrel Non-Disconnect All 2.00-Inch (50.8 mm) and 3.00-Inch (76.2 mm) Diameter CL Fuses



Non-Disconnect (15CXN-GNM-F and 15CXN-GNM-D)



Single Barrel Disconnect All 3.00-Inch (76.2 mm) Diameter CLE Fuses



Disconnect (CX)



Non-Disconnect (15CXN-GNM-G)



Disconnect (15CXN-GNM-F)



Double Barrel Disconnect All 3.00-Inch (76.2 mm) Diameter CLE Fuses



Single-Barrel Non-Disconnect All 2.00-Inch (50.8 mm) and 3.00-Inch (76.2 mm) Diameter CL Fuses



Disconnect (15CXN-GNM-G)



Effective Date: November 1, 2008

Eaton Terms & Conditions



Contents

Description	*Page*
Terms and Conditions of Sale	**V4-A1-1**
Terms of Payment	**V4-A1-2**
Freight	**V4-A1-3**
Warranty	**V4-A1-3**

Selling Policy (Supersedes Selling Policy 25-000, dated February 20, 2006)

Terms and Conditions of Sale

The Terms and Conditions of Sale set forth herein, and any supplements which may be attached hereto, constitute the full and final expression of the contract for the sale of products or services (hereinafter referred to as Product(s) or Services by Eaton Corporation (hereinafter referred to as Seller) to the Buyer, and supersedes all prior quotations, purchase orders, correspondence or communications whether written or oral between the Seller and the Buyer. Notwithstanding any contrary language in the Buyer's purchase order, correspondence or other form of acknowledgment, Buyer shall be bound by these Terms and Conditions of Sale when it sends a purchase order or otherwise indicates acceptance of this contract, or when it accepts delivery from Seller of the Products or Services.

THE CONTRACT FOR SALE OF THE PRODUCTS OR SERVICES IS EXPRESSLY LIMITED TO THE TERMS AND CONDITIONS OF SALE STATED HEREIN. ANY ADDITIONAL OR DIFFERENT TERMS PROPOSED BY BUYER ARE REJECTED UNLESS EXPRESSLY AGREED TO IN WRITING BY SELLER. No contract shall exist except as herein provided.

Complete Agreement

No amendment or modification hereto nor any statement, representation or warranty not contained herein shall be binding on the Seller unless made in writing by an authorized representative of the Seller. Prior dealings, usage of the trade or a course of performance shall not be relevant to determine the meaning of this contract even though the accepting or acquiescing party had knowledge of the nature of the performance and opportunity for objection.

Quotations

Written quotations are valid for 30 days from its date unless otherwise stated in the quotation or terminated sooner by notice.

Verbal quotations, unless accepted, expire the same day they are made.

A complete signed order must be received by Seller within 20 calendar days of notification of award, otherwise the price and shipment will be subject to re-negotiation.

Termination and Cancellation

Any order may be terminated by the Buyer only by written notice and upon payment of reasonable termination charges, including all costs plus profit.

Seller shall have the right to cancel any order at any time by written notice if Buyer breaches any of the terms hereof, becomes the subject of any proceeding under state or federal law for the relief of debtors, or otherwise becomes insolvent or bankrupt, generally does not pay its debts as they become due or makes an assignment for the benefit of creditors.

Appendix 1—Eaton Terms & Conditions

Effective Date: November 1, 2008

Prices

All prices are subject to change without notice. In the event of a price change, the effective date of the change will be the date of the new price or discount sheet, letter or telegram. All quotations made or orders accepted after the effective date will be on the new basis. For existing orders, the price of the unshipped portion of an order will be the price in effect at time of shipment.

Price Policy—Products and Services

When prices are quoted as firm for quoted shipment, they are firm provided the following conditions are met:

1. The order is released with complete engineering details.
2. Shipment of Products are made, and Services purchased are provided within the quoted lead time.
3. When drawings for approval are required for any Products, the drawings applicable to those Products must be returned within 30* calendar days from the date of the original mailing of the drawings by Seller. The return drawings must be released for manufacture and shipment and must be marked "APPROVED" or "APPROVED AS NOTED." Drawing re-submittals which are required for any other reason than to correct Seller errors will not extend the 30-day period.

   * 60 days for orders through contractors to allow time for their review and approval before and after transmitting them to their customers.

If the Buyer initiates or in any way causes delays in shipment, provision of Services or return of approval drawings beyond the periods stated above, the price of the Products or Services will be increased 1% per month or fraction thereof up to a maximum of 18 months from the date of the Buyer's order. For delays resulting in shipment or provision of Services beyond 18 months from the date of the Buyer's order, the price must be renegotiated.

Price Policy—BLS

Refer to Price Policy 25-050.

Minimum Billing

Orders less than $1,000 will be assessed a shipping and handling charge of 5% of the price of the order, with a minimum charge of $25.00 unless noted differently on Product discount sheets.

Taxes

The price does not include any taxes. Buyer shall be responsible for the payment of all taxes applicable to, or arising from the transaction, the Products, its sale, value, or use, or any Services performed in connection therewith regardless of the person or entity actually taxed.

Terms of Payment

Products

Acceptance of all orders is subject to the Buyer meeting Seller's credit requirements. Terms of payment are subject to change for failure to meet such requirements. Seller reserves the right at any time to demand full or partial payment before proceeding with a contract of sale as a result of changes in the financial condition of the Buyer. Terms of Payment are either Net 30 days from the date of invoice of each shipment or carry a cash discount based on Product type. Specific payment terms for Products are outlined in the applicable Product discount schedules.

Services

Terms of payment are net within 30 days from date of invoice for orders amounting to less than $50,000.00.

Terms of payment for orders exceeding $50,000.00 shall be made according to the following:

1. Twenty percent (20%) of order value with the purchase order payable 30 days from date of invoice.
2. Eighty percent (80%) of order value in equal monthly payments over the performance period payable 30 days from date of invoice.

Except for work performed (i) under a firm fixed price basis or (ii) pursuant to terms of a previously priced existing contract between Seller and Buyer, invoices for work performed by Seller shall have added and noted on each invoice a charge of 3% (over and above the price of the work) which is related to Seller compliance with present and proposed environmental, health, and safety regulations associated with prescribed requirements covering hazardous materials management and employee training, communications, personal protective equipment, documentation and record keeping associated therewith.

Adequate Assurances

If, in the judgment of Seller, the financial condition of the Buyer, at any time during the period of the contract, does not justify the terms of payment specified, Seller may require full or partial payment in advance.

Delayed Payment

If payments are not made in accordance with these terms, a service charge will, without prejudice to the right of Seller to immediate payment, be added in an amount equal to the lower of 1.5% per month or fraction thereof or the highest legal rate on the unpaid balance.

Freight

Freight policy will be listed on the Product discount sheets, or at option of Seller one of the following freight terms will be quoted.

F.O.B.—P/S—Frt./Ppd. and Invoiced

Products are sold F.O.B. point of shipment freight prepaid and invoiced to the Buyer.

F.O.B.—P/S—Frt./Ppd. and Allowed

Products sold are delivered F.O.B. point of shipment, freight prepaid and included in the price.

F.O.B. Destination—Frt./Ppd. and Allowed

At Buyer's option, Seller will deliver the Products F.O.B. destination freight prepaid and 2% will be added to the net price.

The term "freight prepaid" means that freight charges will be prepaid to the accessible common carrier delivery point nearest the destination for shipments within the United States and Puerto Rico unless noted differently on the Product discount sheets. For any other destination contact Seller's representative.

Shipment and Routing

Seller shall select the point of origin of shipment, the method of transportation, the type of carrier equipment and the routing of the shipment.

If the Buyer specifies a special method of transportation, type of carrier equipment, routing, or delivery requirement, Buyer shall pay all special freight and handling charges.

When freight is included in the price, no allowance will be made in lieu of transportation if the Buyer accepts shipment at factory, warehouse, or freight station or otherwise supplies its own transportation.

Risk of Loss

Risk of loss or damage to the Products shall pass to Buyer at the F.O.B. point.

Concealed Damage

Except in the event of F.O.B. destination shipments, Seller will not participate in any settlement of claims for concealed damage.

When shipment has been made on an F.O.B. destination basis, the Buyer must unpack immediately and, if damage is discovered must:

1. Not move the Products from the point of examination.
2. Retain shipping container and packing material.
3. Notify the carrier in writing of any apparent damage.
4. Notify Seller representative within 72 hours of delivery.
5. Send Seller a copy of the carrier's inspection report.

Witness Tests/Customer Inspection

Standard factory tests may be witnessed by the Buyer at Seller's factory for an additional charge calculated at the rate of $2,500 per day (not to exceed eight (8) hours) per Product type. Buyer may final inspect Products at the Seller's factory for $500 per day per Product type.

Witness tests will add one (1) week to the scheduled shipping date. Seller will notify Buyer fourteen (14) calendar days prior to scheduled witness testing or inspection. In the event Buyer is unable to attend, the Parties shall mutually agree on a rescheduled date. However, Seller reserves the right to deem the witness tests waived with the right to ship and invoice Products.

Held Orders

For any order held, delayed or rescheduled at the request of the Buyer, Seller may, at its sole option (1) require payment to be based on any reasonable basis, including but not limited to the contract price, and any additional expenses, or cost resulting from such a delay; (2) store Products at the sole cost and risk of loss of the Buyer; and/or (3) charge to the Buyer those prices under the applicable price policy. Payment for such price, expenses and costs, in any such event, shall be due by Buyer within thirty (30) days from date of Seller's invoice. Any order so held delayed or rescheduled beyond six (6) months will be treated as a Buyer termination.

Drawing Approval

Seller will design the Products in line with, in Seller's judgment, good commercial practice. If at drawing approval Buyer makes changes outside of the design as covered in their specifications, Seller will then be paid reasonable charges and allowed a commensurate delay in shipping date based on the changes made.

Drawing Re-Submittal

When Seller agrees to do so in its quotation, Seller shall provide Buyer with the first set of factory customer approval drawing(s) at Seller's expense. The customer approval drawing(s) will be delivered at the quoted delivery date. If Buyer requests drawing changes or additions after the initial factory customer approval drawing(s) have been submitted by Seller, the Seller, at its option, may assess Buyer drawing charges. Factory customer approval drawing changes required due to misinterpretation by Seller will be at Seller's expense. Approval drawings generated by Bid Manager are excluded from this provision.

Warranty

Warranty for Products

Seller warrants that the Products manufactured by it will conform to Seller's applicable specifications and be free from failure due to defects in workmanship and material for one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

In the event any Product fails to comply with the foregoing warranty Seller will, at its option, either (a) repair or replace the defective Product, or defective part or component thereof, F.O.B. Seller's facility freight prepaid, or (b) credit Buyer for the purchase price of the Product. All warranty claims shall be made in writing.

Seller requires all non-conforming Products be returned at Seller's expense for evaluation unless specifically stated otherwise in writing by Seller.

This warranty does not cover failure or damage due to storage, installation, operation or maintenance not in conformance with Seller's recommendations and industry standard practice or due to accident, misuse, abuse or negligence. This warranty does not cover reimbursement for labor, gaining access, removal, installation, temporary power or any other expenses, which may be incurred in connection with repair or replacement.

This warranty does not apply to equipment not manufactured by Seller. Seller limits itself to extending the same warranty it receives from the supplier.

Appendix 1—Eaton Terms & Conditions

Effective Date: November 1, 2008

Extended Warranty for Products

If requested by the Buyer and specifically accepted in writing by Seller, the foregoing standard warranty for Products will be extended from the date of shipment for the period and price indicated below:

- 24 months—2% of Contract Price
- 30 months—3% of Contract Price
- 36 months—4% of Contract Price

Special Warranty (In and Out) for Products

If requested by the Buyer and specifically accepted in writing by Seller, Seller will, during the warranty period for Products, at an additional cost of 2% of the contract price, be responsible for the direct cost of:

1. Removing the Product from the installed location.
2. Transportation to the repair facility and return to the site.
3. Reinstallation on site.

The total liability of Seller for this Special Warranty for Products is limited to 50% of the contract price of the particular Product being repaired and excludes expenses for removing adjacent apparatus, walls, piping, structures, temporary service, etc.

Warranty for Services

Seller warrants that the Services performed by it hereunder will be performed in accordance with generally accepted professional standards.

The Services, which do not so conform, shall be corrected by Seller upon notification in writing by the Buyer within one (1) year after completion of the Services.

Unless otherwise agreed to in writing by Seller, Seller assumes no responsibility with respect to the suitability of the Buyer's, or its customer's, equipment or with respect to any latent defects in equipment not supplied by Seller. This warranty does not cover damage to Buyer's, or its customer's, equipment, components or parts resulting in whole or in part from improper maintenance or operation or from their deteriorated condition. Buyer will, at its cost, provide Seller with unobstructed access to the defective Services, as well as adequate free working space in the immediate vicinity of the defective Services and such facilities and systems, including, without limitation, docks, cranes and utility disconnects and connects, as may be necessary in order that Seller may perform its warranty obligations. The conducting of any tests shall be mutually agreed upon and Seller shall be notified of, and may be present at, all tests that may be made.

Warranty for Power Systems Studies

Seller warrants that any power systems studies performed by it will conform to generally accepted professional standards. Any portion of the study, which does not so conform, shall be corrected by Seller upon notification in writing by the Buyer within six (6) months after completion of the study. All warranty work shall be performed in a single shift straight time basis Monday through Friday. In the event that the study requires correction of warranty items on an overtime schedule, the premium portion of such overtime shall be for the Buyer's account.

Limitation on Warranties for Products, Services and Power Systems Studies

THE FOREGOING WARRANTIES ARE EXCLUSIVE EXCEPT FOR WARRANTY OF TITLE. SELLER DISCLAIMS ALL OTHER WARRANTIES INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

CORRECTION OF NON-CONFORMITIES IN THE MANNER AND FOR THE PERIOD OF TIME PROVIDED ABOVE SHALL CONSTITUTE SELLER'S SOLE LIABILITY AND BUYER'S EXCLUSIVE REMEDY FOR FAILURE OF SELLER TO MEET ITS WARRANTY OBLIGATIONS, WHETHER CLAIMS OF THE BUYER ARE BASED IN CONTRACT, IN TORT (INCLUDING NEGLIGENCE OR STRICT LIABILITY), OR OTHERWISE.

Asbestos

Federal Law requires that building or facility owners identify the presence, location and quantity of asbestos containing material (hereinafter "ACM") at work sites. Seller is not licensed to abate ACM. Accordingly, for any contract which includes the provision of Services, prior to (i) commencement of work at any site under a specific Purchase Order, (ii) a change in the work scope of any Purchase Order, the Buyer will certify that the work area associated with the Seller's scope of work includes the handling of Class II ACM, including but not limited to generator wedges and high temperature gaskets which include asbestos materials. The Buyer shall, at its expense, conduct abatement should the removal, handling, modification or reinstallation, or some or all of them, of said Class II ACM be likely to generate airborne asbestos fibers; and should such abatement affect the cost of or time of performance of the work then Seller shall be entitled to an equitable adjustment in the schedule, price and other pertinent affected provisions of the contract.

Compliance with Nuclear Regulation

Seller's Products are sold as commercial grade Products not intended for application in facilities or activities licensed by the United States Nuclear Regulatory Commission for atomic purposes. Further certification will be required for use of the Products in any safety-related application in any nuclear facility licensed by the U.S. Nuclear Regulatory Commission.

Returning Products

Authorization and shipping instructions for the return of any Products must be obtained from Seller before returning the Products.

When return is occasioned due to Seller error, full credit including all transportation charges will be allowed.

Product Notices

Buyer shall provide the user (including its employees) of the Products with all Seller supplied Product notices, warnings, instructions, recommendations, and similar materials.

Force Majeure

Seller shall not be liable for failure to perform or delay in performance due to fire, flood, strike or other labor difficulty, act of God, act of any governmental authority or of the Buyer, riot, embargo, fuel or energy shortage, car shortage, wrecks or delays in transportation, or due to any other cause beyond Seller's reasonable control. In the event of delay in performance due to any such cause, the date of delivery or time for completion will be extended by a period of time reasonably necessary to overcome the effect of such delay.

Liquidated Damages

Contracts which include liquidated damage clauses for failure to meet shipping or job completion promises are not acceptable or binding on Seller, unless such clauses are specifically accepted in writing by an authorized representative of the Seller at its headquarters office.

Patent Infringement

Seller will defend or, at its option, settle any suit or proceeding brought against Buyer, or Buyer's customers, to the extent it is based upon a claim that any Product or part thereof, manufactured by Seller or its subsidiaries and furnished hereunder, infringes any United States patent, other than a claim of infringement based upon use of a Product or part thereof in a process, provided Seller is notified in reasonable time and given authority, information and assistance (at Seller's expense) for the defense of same. Seller shall pay all legal and court costs and expenses and court-assessed damages awarded therein against Buyer resulting from or incident to such suit or proceeding. In addition to the foregoing, if at any time Seller determines there is a substantial question of infringement of any United States patent, and the use of such Product is or may be enjoined, Seller may, at its option and expense: either (a) procure for Buyer the right to continue using and selling the Product; (b) replace the Product with non-infringing apparatus; (c) modify the Product so it becomes non-infringing; or (d) as a last resort, remove the Product and refund the purchase price, equitably adjusted for use and obsolescence. In no case does Seller agree to pay any recovery based upon its Buyer's savings or profit through use of Seller's Products whether the use be special or ordinary. The foregoing states the entire liability of Seller for patent infringement.

The preceding paragraph does not apply to any claim of infringement based upon: (a) any modification made to a Product other than by Seller; (b) any design and/or specifications of Buyer to which a Product was manufactured; or (c) the use or combination of Product with other products where the Product does not itself infringe. As to the above-identified claim situations where the preceding paragraph does not apply, Buyer shall defend and hold Seller harmless in the same manner and to the extent as Seller's obligations described in the preceding paragraph. Buyer shall be responsible for obtaining (at Buyer's expense) all license rights required for Seller to be able to use software products in the possession of Buyer where such use is required in order to perform any Service for Buyer.

With respect to a Product or part thereof not manufactured by Seller or its subsidiaries, Seller will attempt to obtain for Buyer, from the supplier(s), the patent indemnification protection normally provided by the supplier(s) to customers.

Compliance with OSHA

Seller offers no warranty and makes no representation that its Products comply with the provisions or standards of the Occupational Safety and Health Act of 1970, or any regulation issued thereunder. In no event shall Seller be liable for any loss, damage, fines, penalty or expenses arising under said Act.

Limitation of Liability

THE REMEDIES OF THE BUYER SET FORTH IN THIS CONTRACT ARE EXCLUSIVE AND ARE ITS SOLE REMEDIES FOR ANY FAILURE OF SELLER TO COMPLY WITH ITS OBLIGATIONS HEREUNDER.

NOTWITHSTANDING ANY PROVISION IN THIS CONTRACT TO THE CONTRARY, IN NO EVENT SHALL SELLER BE LIABLE IN CONTRACT, IN TORT (INCLUDING NEGLIGENCE OR STRICT LIABILITY) OR OTHERWISE FOR DAMAGE TO PROPERTY OR EQUIPMENT OTHER THAN PRODUCTS SOLD HEREUNDER, LOSS OF PROFITS OR REVENUE, LOSS OF USE OF PRODUCTS, COST OF

CAPITAL, CLAIMS OF CUSTOMERS OF THE BUYER OR ANY SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES WHATSOEVER, REGARDLESS OF WHETHER SUCH POTENTIAL DAMAGES ARE FORESEEABLE OR IF SELLER HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

THE TOTAL CUMULATIVE LIABILITY OF SELLER ARISING FROM OR RELATED TO THIS CONTRACT WHETHER THE CLAIMS ARE BASED IN CONTRACT, IN TORT (INCLUDING NEGLIGENCE OR STRICT LIABILITY) OR OTHERWISE, SHALL NOT EXCEED THE PRICE OF THE PRODUCT OR SERVICES ON WHICH SUCH LIABILITY IS BASED.

A

AAL V4-**T2**-279, V4-**T2**-368
AA1 . . . . . V4-**T2**-109, V4-**T2**-368
AA11 . . . . . V4-**T2**-280
AA21 . . . . . V4-**T2**-280
AA31 . . . . . V4-**T2**-280
ALM V4-**T2**-109, V4-**T2**-368, V4-**T2**-395
AUX. V4-**T2**-109, V4-**T2**-368, V4-**T2**-395, V4-**T2**-430
A1L V4-**T2**-109, V4-**T2**-275, V4-**T2**-276, V4-**T2**-368, V4-**T2**-395
A1X V4-**T2**-109, V4-**T2**-277, V4-**T2**-278, V4-**T2**-347, V4-**T2**-368, V4-**T2**-395
A2L V4-**T2**-109, V4-**T2**-275, V4-**T2**-276, V4-**T2**-395
A2X V4-**T2**-109, V4-**T2**-277, V4-**T2**-278, V4-**T2**-347, V4-**T2**-368, V4-**T2**-395
A3X V4-**T2**-109, V4-**T2**-278
A4X V4-**T2**-109, V4-**T2**-278, V4-**T2**-395

B

BAB. V4-**T1**-12, V4-**T1**-32, V4-**T1**-38, V4-**T1**-41–V4-**T1**-45
BBMK V4-**T2**-320
BB-UL V4-**T1**-79, V4-**T1**-80
BIM V4-**T2**-327
BMH V4-**T2**-69, V4-**T2**-313, V4-**T2**-336, V4-**T2**-367
BRR. V4-**T1**-32
B20 . . . . . V4-**T2**-80
B201 . . . . . V4-**T2**-249, V4-**T2**-357
B25 . . . . . V4-**T2**-80
B250 . . . . . V4-**T2**-249, V4-**T2**-357
B300 . . . . . V4-**T2**-357

C

CFDPV. V4-**T2**-366
CHK. V4-**T2**-166
CHKD V4-**T2**-176, V4-**T2**-178
CHL V4-**T2**-189
CHLD. V4-**T2**-198, V4-**T2**-201
CHMDL V4-**T2**-215
CHND V4-**T2**-227, V4-**T2**-229
CJGPVS. V4-**T2**-365
CKD. V4-**T2**-166, V4-**T2**-175, V4-**T2**-177
CKDPV. V4-**T2**-366
CKDPVS V4-**T2**-365
CLD V4-**T2**-189, V4-**T2**-197, V4-**T2**-200
CLDC. V4-**T2**-199, V4-**T2**-202
CLE V4-**T3**-117–V4-**T3**-123, V4-**T3**-134
CLGPV. V4-**T2**-366
CLPT V4-**T3**-136–V4-**T3**-139
CLR V4-**T1**-32
CMDL V4-**T2**-215
CMDLPV V4-**T2**-366
CND. V4-**T2**-227, V4-**T2**-229
CNDC V4-**T2**-228, V4-**T2**-230
CRD. V4-**T2**-240, V4-**T2**-242, V4-**T2**-244, V4-**T2**-246, V4-**T2**-248
CTF V4-**T2**-150
CTK V4-**T2**-107, V4-**T2**-318
CX V4-**T3**-140–V4-**T3**-143, V4-**T3**-146
CXN V4-**T3**-146
C361 . . . . . V4-**T2**-328, V4-**T2**-430
C37 . . . . . V4-**T2**-445
C371 . . . . . V4-**T2**-444

D

DBU V4-**T3**-109, V4-**T3**-110
DBU17 . . . . . V4-**T3**-108
DBU27 . . . . . V4-**T3**-109
DBU38 . . . . . V4-**T3**-110
DIGI V4-**T2**-36, V4-**T2**-52, V4-**T2**-69, V4-**T2**-81, V4-**T2**-106, V4-**T2**-150, V4-**T2**-327
DK V4-**T2**-167, V4-**T2**-168
DOPT V4-**T2**-326

E

ED V4-**T2**-138
EDB V4-**T2**-139
EDC V4-**T2**-139
EDH V4-**T2**-138
EDS V4-**T2**-140
EEC V4-**T2**-25
EFH V4-**T2**-107
EFP V4-**T2**-107
EFS V4-**T2**-107
EFT. V4-**T2**-25, V4-**T2**-114
EF1. . . . . V4-**T2**-25
EF3. . . . . V4-**T2**-25
EGB V4-**T2**-17, V4-**T2**-22
EGC V4-**T2**-21, V4-**T2**-97
EGD V4-**T2**-25
EGE V4-**T2**-18, V4-**T2**-352
EGF V4-**T2**-429
EGG V4-**T2**-25
EGH V4-**T2**-20, V4-**T2**-23, V4-**T2**-352, V4-**T2**-421
EGK V4-**T2**-21
EGS V4-**T2**-19, V4-**T2**-22, V4-**T2**-352
EG3 . . . . . V4-**T2**-107
EG4 . . . . . V4-**T2**-107
EHD V4-**T2**-140, V4-**T2**-146
EHM. V4-**T2**-426, V4-**T2**-427, V4-**T2**-429
EIP V4-**T2**-25, V4-**T2**-97
ELC V4-**T2**-269
ELE V4-**T2**-93
ELJ. V4-**T2**-93
ELL. V4-**T2**-93
EOP V4-**T2**-107, V4-**T2**-320, V4-**T2**-321
EOP5 . . . . . V4-**T2**-321
E1X1 . . . . . V4-**T2**-277
E2. . . . . V4-**T2**-382–V4-**T2**-392
E2X1 . . . . . V4-**T2**-277

F

FAZ-B. V4-**T1**-51, V4-**T1**-72
FAZ-C. V4-**T1**-52–V4-**T1**-54, V4-**T1**-72, V4-**T1**-73
FAZ-D V4-**T1**-53, V4-**T1**-74
FAZ-K. V4-**T1**-75
FAZP V4-**T1**-58
FAZ-S. V4-**T1**-76
FAZ-X. V4-**T1**-78
FAZ-XAA V4-**T1**-58, V4-**T1**-78
FAZ-XUA V4-**T1**-78
FAZ-Z. V4-**T1**-77
FCWT V4-**T2**-311
FD V4-**T2**-141, V4-**T2**-142, V4-**T2**-146
FDC V4-**T2**-144, V4-**T2**-145, V4-**T2**-271
FDE V4-**T2**-145
FDMP V4-**T2**-268
FDPV. V4-**T2**-366
FD1 . . . . . V4-**T2**-142
FD2 . . . . . V4-**T2**-142
FD3 . . . . . V4-**T2**-142
FD4 . . . . . V4-**T2**-142
FG V4-**T2**-345
FHMV V4-**T2**-440
FJC V4-**T2**-41
FJH V4-**T2**-426
FJI V4-**T2**-41
FJP V4-**T2**-107
FJS V4-**T2**-107
FJT. V4-**T2**-41, V4-**T2**-114
FJ3. . . . . V4-**T2**-41, V4-**T2**-341
FJ4. . . . . V4-**T2**-41
FPH V4-**T2**-338
FPS V4-**T2**-338
F0S0 . . . . . V4-**T2**-444
F1S0 . . . . . V4-**T2**-444
F1S1 . . . . . V4-**T2**-444
F2S0 . . . . . V4-**T2**-444
F2S1 . . . . . V4-**T2**-444
F3S0 . . . . . V4-**T2**-444
F3S1 . . . . . V4-**T2**-444
F4S0 . . . . . V4-**T2**-444
F4S1 . . . . . V4-**T2**-444
F5S V4-**T2**-429
F5S0 . . . . . V4-**T2**-429, V4-**T2**-444
F5S1 . . . . . V4-**T2**-444
F6S0 . . . . . V4-**T2**-429, V4-**T2**-444
F7S0 . . . . . V4-**T2**-444
F7S1 . . . . . V4-**T2**-444

G

GBHS. V4-**T1**-35
GCH. V4-**T2**-434
GCWT V4-**T2**-312
GD V4-**T2**-123, V4-**T2**-124
GDB. V4-**T2**-124
GFAU V4-**T2**-326
GFMB V4-**T1**-38
GFR V4-**T2**-417, V4-**T2**-418
GHB V4-**T2**-127, V4-**T2**-129, V4-**T2**-134
GHBS. V4-**T1**-35
GHC V4-**T2**-132–V4-**T2**-134
GHMV V4-**T2**-440
GHQ. V4-**T1**-35
GKOA. V4-**T2**-315
GMCP V4-**T2**-258
GMH V4-**T2**-259, V4-**T2**-434
GPHB. V4-**T2**-316
GPS V4-**T2**-338
GTSK V4-**T2**-314

H

HBA V4-**T1**-13
HCL V4-**T3**-127
HEX V4-**T2**-58, V4-**T2**-69, V4-**T2**-80, V4-**T2**-446
HFD V4-**T2**-143, V4-**T2**-145, V4-**T2**-146, V4-**T2**-353
HFDMP V4-**T2**-268
HGHB. V4-**T2**-127
HGHC. V4-**T2**-132
HJD V4-**T2**-155, V4-**T2**-156, V4-**T2**-354
HKD V4-**T2**-164–V4-**T2**-165, V4-**T2**-166, V4-**T2**-168, V4-**T2**-170, V4-**T2**-173, V4-**T2**-355
HLD V4-**T2**-188–V4-**T2**-189, V4-**T2**-190, V4-**T2**-192, V4-**T2**-195, V4-**T2**-356
HLK V4-**T2**-107, V4-**T2**-317, V4-**T2**-393
HM. V4-**T2**-438
HMC V4-**T2**-442
HMCP V4-**T2**-86–V4-**T2**-88, V4-**T2**-260, V4-**T2**-261, V4-**T2**-263–V4-**T2**-266
HMCPS V4-**T2**-262
HMDL V4-**T2**-213–V4-**T2**-216, V4-**T2**-357
HMV. V4-**T2**-426, V4-**T2**-442
HND V4-**T2**-224, V4-**T2**-226, V4-**T2**-230
HQP V4-**T1**-6, V4-**T1**-41–V4-**T1**-45
HRG V4-**T2**-259, V4-**T2**-442

I

ICK V4-**T2**-293
INK. V4-**T2**-347
IPB V4-**T2**-58, V4-**T2**-69, V4-**T2**-315, V4-**T2**-367

J

JD V4-**T2**-155, V4-**T2**-156
JDB V4-**T2**-156
JDC V4-**T2**-155, V4-**T2**-156
JFDN V4-**T2**-347
JG V4-**T2**-345
JGC V4-**T2**-33, V4-**T2**-35, V4-**T2**-38
JGE V4-**T2**-31, V4-**T2**-35, V4-**T2**-37, V4-**T2**-39, V4-**T2**-40, V4-**T2**-353
JGF V4-**T2**-36–V4-**T2**-38, V4-**T2**-40, V4-**T2**-81, V4-**T2**-429

JGH V4-**T2**-32, V4-**T2**-35, V4-**T2**-37, V4-**T2**-39, V4-**T2**-40, V4-**T2**-354, V4-**T2**-421
JGK V4-**T2**-34
JGMP V4-**T2**-90
JGPVS V4-**T2**-365
JGS V4-**T2**-31, V4-**T2**-35, V4-**T2**-37, V4-**T2**-39, V4-**T2**-40, V4-**T2**-354
JGU V4-**T2**-33, V4-**T2**-35, V4-**T2**-38
JGX V4-**T2**-34, V4-**T2**-35, V4-**T2**-38
JG3 . . . . . V4-**T2**-107, V4-**T2**-115
JG4 . . . . . V4-**T2**-107, V4-**T2**-115
JHM V4-**T2**-427, V4-**T2**-429
JHMV V4-**T2**-440
JJDN V4-**T2**-347
JKDN V4-**T2**-347
JLDN V4-**T2**-347
JNDN V4-**T2**-347
JT V4-**T2**-155
JT2 . . . . . V4-**T2**-35
JT3 . . . . . V4-**T2**-35, V4-**T2**-36, V4-**T2**-353, V4-**T2**-354
JT4 . . . . . V4-**T2**-35, V4-**T2**-36

K

KCWT V4-**T2**-311
KD V4-**T2**-164–V4-**T2**-166, V4-**T2**-167, V4-**T2**-168, V4-**T2**-169, V4-**T2**-172
KDB V4-**T2**-166, V4-**T2**-168
KDC V4-**T2**-164–V4-**T2**-165, V4-**T2**-171, V4-**T2**-174
KDPV V4-**T2**-366
KDPVS V4-**T2**-365
KES V4-**T2**-165, V4-**T2**-166
KG V4-**T2**-345
KHMV V4-**T2**-440
KLH V4-**T2**-426
KPE V4-**T2**-341, V4-**T2**-369
KPEK V4-**T2**-310, V4-**T2**-393
KPEM V4-**T2**-393
KPR V4-**T2**-310
KPS V4-**T2**-339
KT V4-**T2**-164, V4-**T2**-355
KYK V4-**T2**-107, V4-**T2**-318

L

LBH V4-**T2**-107
LD V4-**T2**-188–V4-**T2**-189, V4-**T2**-190, V4-**T2**-191, V4-**T2**-194, V4-**T2**-196
LDB V4-**T2**-189, V4-**T2**-190
LDC V4-**T2**-189, V4-**T2**-193, V4-**T2**-196
LES V4-**T2**-189
LFD V4-**T2**-326
LG V4-**T2**-346
LGC V4-**T2**-50, V4-**T2**-51, V4-**T2**-54, V4-**T2**-57
LGE V4-**T2**-49, V4-**T2**-51, V4-**T2**-53, V4-**T2**-55–V4-**T2**-57, V4-**T2**-355
LGF V4-**T2**-52–V4-**T2**-54, V4-**T2**-56, V4-**T2**-57
LGH V4-**T2**-49, V4-**T2**-51, V4-**T2**-53, V4-**T2**-55–V4-**T2**-57, V4-**T2**-356, V4-**T2**-421
LGK V4-**T2**-51
LGMP V4-**T2**-90
LGPV V4-**T2**-366
LGS V4-**T2**-49, V4-**T2**-51, V4-**T2**-53, V4-**T2**-55, V4-**T2**-56, V4-**T2**-57, V4-**T2**-107, V4-**T2**-355
LGT V4-**T2**-58
LGU V4-**T2**-50, V4-**T2**-51, V4-**T2**-54, V4-**T2**-57
LGX V4-**T2**-50, V4-**T2**-51, V4-**T2**-54, V4-**T2**-57
LG3 . . . . . V4-**T2**-107, V4-**T2**-115
LG4 . . . . . V4-**T2**-107, V4-**T2**-115
LHH V4-**T2**-102
LHM V4-**T2**-427, V4-**T2**-429
LHMV V4-**T2**-440
LKD V4-**T2**-107, V4-**T2**-316, V4-**T2**-367
LPH V4-**T2**-107, V4-**T2**-339, V4-**T2**-393
LPS V4-**T2**-339
LST V4-**T2**-110, V4-**T2**-285
LT V4-**T2**-188, V4-**T2**-355, V4-**T2**-356
LTS V4-**T2**-58, V4-**T2**-114
LT3 . . . . . V4-**T2**-51, V4-**T2**-52, V4-**T2**-57, V4-**T2**-355
LT4 . . . . . V4-**T2**-51, V4-**T2**-52, V4-**T2**-355
L3R V4-**T2**-58, V4-**T2**-341, V4-**T2**-393
L4R V4-**T2**-58, V4-**T2**-369

M

MA V4-**T3**-13
MAA V4-**T2**-279
MA1 . . . . . V4-**T2**-275
MA2 . . . . . V4-**T2**-275
MB V4-**T3**-13
MD V4-**T3**-13
MDL V4-**T2**-213, V4-**T2**-215, V4-**T2**-216
MDLB V4-**T2**-214
MDLPV V4-**T2**-366
MES V4-**T2**-215
MOP V4-**T2**-107, V4-**T2**-113, V4-**T2**-320
MPS V4-**T2**-339
MT V4-**T2**-213, V4-**T2**-357
MTS V4-**T2**-36, V4-**T2**-52, V4-**T2**-69, V4-**T2**-81, V4-**T2**-106
MTST V4-**T2**-150
MUVH V4-**T2**-288

N

NB V4-**T2**-357
ND V4-**T2**-224, V4-**T2**-226, V4-**T2**-230
NDC V4-**T2**-225, V4-**T2**-226
NG V4-**T2**-346
NGF V4-**T2**-69
NGH V4-**T2**-67, V4-**T2**-68, V4-**T2**-422
NGU V4-**T2**-68

NG3 . . . . . V4-**T2**-115
NG4 . . . . . V4-**T2**-115
NHH. V4-**T2**-102
NTS V4-**T2**-69
NTS3 . . . . . V4-**T2**-315

O

OPTIM. V4-**T2**-327
ORPK. V4-**T2**-169–V4-**T2**-178
ORPL. V4-**T2**-191–V4-**T2**-202
ORPN V4-**T2**-224–V4-**T2**-230
ORPR. V4-**T2**-247, V4-**T2**-248

P

PAD V4-**T2**-107, V4-**T2**-114, V4-**T2**-321, V4-**T2**-322
PHB V4-**T2**-316
PHL V4-**T2**-316, V4-**T2**-317
PIIL V4-**T2**-114
PLK V4-**T2**-107, V4-**T2**-317, V4-**T2**-367, V4-**T2**-393
PLN2 . . . . . V4-**T2**-311
PMP. V4-**T2**-321
PM3. . . . . V4-**T2**-341
PRTB V4-**T2**-327

Q

QBAF. V4-**T1**-15
QBCAF V4-**T1**-15
QBGF. V4-**T1**-18, V4-**T1**-19
QBH. V4-**T1**-12, V4-**T1**-15
QC V4-**T1**-21, V4-**T1**-41–V4-**T1**-45
QCD. V4-**T1**-23
QCF V4-**T1**-26, V4-**T1**-44
QCG. V4-**T1**-29
QCH. V4-**T1**-29
QCHW. V4-**T1**-22
QCR. V4-**T1**-25, V4-**T1**-27
QHCW. V4-**T1**-22
QHCX V4-**T1**-22
QHP. V4-**T1**-7
QL V4-**T1**-43, V4-**T1**-45, V4-**T1**-46
QPGF. V4-**T1**-9, V4-**T1**-10, V4-**T1**-18
QPH. V4-**T1**-6
QPHG V4-**T1**-9

R

RBA2 . . . . . V4-**T3**-96, V4-**T3**-99, V4-**T3**-102, V4-**T3**-105
RBA4 . . . . . V4-**T3**-97, V4-**T3**-98, V4-**T3**-100, V4-**T3**-101, V4-**T3**-103, V4-**T3**-104, V4-**T3**-106, V4-**T3**-107
RD V4-**T2**-239, V4-**T2**-241, V4-**T2**-243, V4-**T2**-245, V4-**T2**-247, V4-**T2**-248
RDB2. . . . . V4-**T3**-96–V4-**T3**-105
RDB4. . . . . V4-**T3**-97, V4-**T3**-100, V4-**T3**-103, V4-**T3**-106
RDB8. . . . . V4-**T3**-98–V4-**T3**-107
RDC. V4-**T2**-239, V4-**T2**-241, V4-**T2**-243, V4-**T2**-245, V4-**T2**-247
RFDN. V4-**T2**-347
RG V4-**T2**-357
RGC V4-**T2**-77–V4-**T2**-79
RGH V4-**T2**-76, V4-**T2**-78, V4-**T2**-79, V4-**T2**-422
RGK V4-**T2**-77
RJDN V4-**T2**-347
RKDN V4-**T2**-347
RLDN V4-**T2**-347
RNDN. V4-**T2**-347
RP6R V4-**T2**-78, V4-**T2**-79, V4-**T2**-239–V4-**T2**-246

S

SBK V4-**T2**-107, V4-**T2**-319
SFDN V4-**T2**-347
SJDN V4-**T2**-347
SKDN V4-**T2**-347
SLA V4-**T3**-76
SLBK V4-**T1**-32
SLDN V4-**T2**-347
SNDN. V4-**T2**-347
SNT V4-**T2**-110, V4-**T2**-347
SNT1 . . . . . V4-**T2**-281, V4-**T2**-368, V4-**T2**-395
SNT2 . . . . . V4-**T2**-282, V4-**T2**-395
SNT3 . . . . . V4-**T2**-282, V4-**T2**-368, V4-**T2**-395
SNT4 . . . . . V4-**T2**-283, V4-**T2**-395
SNT5 . . . . . V4-**T2**-284, V4-**T2**-395
SNT6 . . . . . V4-**T2**-284, V4-**T2**-395
STK2 . . . . . V4-**T2**-326

T

TAD3 . . . . . V4-**T2**-311
TA1 . . . . . V4-**T2**-69, V4-**T2**-80, V4-**T3**-45, V4-**T3**-52
TA10 . . . . . V4-**T2**-231, V4-**T2**-347, V4-**T2**-357, V4-**T2**-408
TA12 . . . . . V4-**T2**-231, V4-**T2**-347, V4-**T2**-357, V4-**T2**-408
TA16 . . . . . V4-**T2**-249, V4-**T2**-393
TA2 . . . . . V4-**T2**-80, V4-**T2**-408
TA20 . . . . . V4-**T2**-249, V4-**T2**-393
TA25 . . . . . V4-**T2**-41, V4-**T2**-155–V4-**T2**-157, V4-**T2**-347
TA250 . . . . . V4-**T2**-99
TA3 . . . . . V4-**T2**-369
TA30 . . . . . V4-**T2**-164, V4-**T2**-179, V4-**T2**-355
TA35 . . . . . V4-**T2**-58, V4-**T2**-164, V4-**T2**-179, V4-**T2**-336, V4-**T2**-347, V4-**T2**-355, V4-**T2**-356
TA40 . . . . . V4-**T2**-408
TA45 . . . . . V4-**T2**-203
TA60 . . . . . V4-**T2**-188, V4-**T2**-203, V4-**T2**-311, V4-**T2**-336, V4-**T2**-356, V4-**T2**-408
TA7 . . . . . V4-**T2**-69, V4-**T2**-369, V4-**T3**-45, V4-**T3**-52
TA70 . . . . . V4-**T2**-213, V4-**T2**-214, V4-**T2**-217, V4-**T2**-231, V4-**T2**-347, V4-**T2**-357, V4-**T2**-393, V4-**T2**-408
TA8 . . . . . V4-**T2**-369
TA80 . . . . . V4-**T2**-213, V4-**T2**-214, V4-**T2**-217, V4-**T2**-357, V4-**T2**-393, V4-**T2**-408
TBRD V4-**T2**-293
TEC V4-**T2**-315
TRIP V4-**T2**-36, V4-**T2**-52, V4-**T2**-69, V4-**T2**-106, V4-**T2**-150, V4-**T2**-327

TS33 . . . . . V4-**T2**-315
TS34 . . . . . V4-**T2**-315
T10 . . . . . V4-**T2**-69
T100 . . . . . V4-**T2**-231, V4-**T2**-393, V4-**T2**-408
T12 . . . . . V4-**T2**-69, V4-**T2**-97
T120 . . . . . V4-**T2**-231, V4-**T2**-393, V4-**T2**-408
T16 . . . . . V4-**T2**-80, V4-**T2**-249
T225 . . . . . V4-**T2**-408
T250 . . . . . V4-**T2**-41, V4-**T2**-157, V4-**T2**-271, V4-**T2**-353, V4-**T2**-354, V4-**T2**-393
T30 . . . . . V4-**T2**-369
T300 . . . . . V4-**T2**-179, V4-**T2**-393
T35 . . . . . V4-**T2**-369
T350 . . . . . V4-**T2**-58, V4-**T2**-179, V4-**T2**-393, V4-**T2**-408
T401 . . . . . V4-**T2**-408
T600 . . . . . V4-**T2**-217, V4-**T2**-393, V4-**T2**-408
T602 . . . . . V4-**T2**-203, V4-**T2**-311, V4-**T2**-393
T70 . . . . . V4-**T2**-69
T700 . . . . . V4-**T2**-231, V4-**T2**-393
T800 . . . . . V4-**T2**-217, V4-**T2**-393, V4-**T2**-408

U

UVH. V4-**T2**-110, V4-**T2**-288–V4-**T2**-292, V4-**T2**-368, V4-**T2**-394
UVM V4-**T2**-394
UVR. V4-**T2**-110, V4-**T2**-368

W

WBL V4-**T2**-107, V4-**T2**-319
WHM. V4-**T2**-438

Z

Z-EB. V4-**T1**-58
Z-EK. V4-**T1**-58
ZGK V4-**T2**-293
ZGPK V4-**T2**-293
Z-IS V4-**T1**-58
Z-NH V4-**T1**-58, V4-**T1**-92, V4-**T1**-98
Z-SV. V4-**T1**-58
ZV-BS V4-**T1**-58

Numerics

05B7 . . . . . V4-**T2**-409
1223 . . . . . V4-**T2**-316
1225 . . . . . V4-**T2**-259, V4-**T2**-315
1227 . . . . . V4-**T2**-405, V4-**T2**-406
1228 . . . . . V4-**T2**-410
1229 . . . . . V4-**T2**-405, V4-**T2**-406
1231 . . . . . V4-**T2**-321
1234 . . . . . V4-**T2**-418
1241 . . . . . V4-**T2**-409
1253 . . . . . V4-**T2**-324
1255 . . . . . V4-**T2**-417
1256 . . . . . V4-**T2**-417
1257 . . . . . V4-**T2**-417
1260. . . . . V4-**T2**-321
1261. . . . . V4-**T2**-409
1262. . . . . V4-**T2**-409
1264. . . . . V4-**T2**-326, V4-**T2**-407
1266. . . . . V4-**T2**-314
1283. . . . . V4-**T2**-417
1288. . . . . V4-**T2**-259, V4-**T2**-275, V4-**T2**-277, V4-**T2**-322
1290. . . . . V4-**T2**-322
1291. . . . . V4-**T2**-404, V4-**T2**-406
1294. . . . . V4-**T2**-259, V4-**T2**-316
1373. . . . . V4-**T2**-259, V4-**T2**-281, V4-**T2**-286
14RB V4-**T3**-96–V4-**T3**-101
1480. . . . . V4-**T2**-321
1482. . . . . V4-**T2**-278, V4-**T2**-279
149. . . . . V4-**T2**-423, V4-**T2**-434
15BH V4-**T3**-123
15BHLE V4-**T3**-123
15CL V4-**T3**-138
15CLE V4-**T3**-120
15CLE2 . . . . . V4-**T3**-120
15CLE3 . . . . . V4-**T3**-120
15CLPT V4-**T3**-138
15CX V4-**T3**-143, V4-**T3**-146
15CXI V4-**T3**-143
15CXN V4-**T3**-144, V4-**T3**-145
15HCL V4-**T3**-127
15HLE V4-**T3**-123
15NC V4-**T3**-138
15RB V4-**T3**-96–V4-**T3**-101
15RBT V4-**T3**-99
15RD V4-**T3**-99–V4-**T3**-101
167. . . . . V4-**T1**-91, V4-**T1**-97
176C V4-**T2**-321
179C V4-**T2**-417
2ACLS V4-**T3**-129
2BCLS V4-**T3**-129
2CLE V4-**T3**-117, V4-**T3**-134
2CLS V4-**T3**-129
2HCLS V4-**T3**-129
2NCL V4-**T3**-135
2TA4 . . . . . V4-**T2**-164, V4-**T2**-179, V4-**T2**-203
2TA6 . . . . . V4-**T2**-188, V4-**T2**-190, V4-**T2**-203, V4-**T2**-311
2T40. . . . . V4-**T2**-179
207B V4-**T2**-315
208B V4-**T2**-315, V4-**T2**-324, V4-**T2**-325
24RB V4-**T3**-102
25CL V4-**T3**-139
25CXN V4-**T3**-145
25RB V4-**T3**-102–V4-**T3**-104
25RD V4-**T3**-102–V4-**T3**-104
2600. . . . . V4-**T2**-324, V4-**T2**-407
2602. . . . . V4-**T2**-407
2603. . . . . V4-**T2**-407
2605. . . . . V4-**T2**-410
2606. . . . . V4-**T2**-410
2609. . . . . V4-**T2**-404–V4-**T2**-407

Appendix 2—Catalog Parent Number Index

2610 . . . . . V4-**T2**-407
2611 . . . . . V4-**T2**-407
2614 . . . . . V4-**T2**-322
3TA V4-**T2**-23–V4-**T2**-25, V4-**T2**-41, V4-**T2**-58, V4-**T2**-369
3TA1 . . . . . V4-**T2**-147, V4-**T2**-312
3TA2 . . . . . V4-**T2**-147, V4-**T2**-271, V4-**T2**-312, V4-**T2**-336, V4-**T2**-347
3TA4 . . . . . V4-**T2**-164, V4-**T2**-179, V4-**T2**-203, V4-**T2**-312, V4-**T2**-336, V4-**T2**-347, V4-**T2**-355, V4-**T2**-393
3TA5 . . . . . V4-**T2**-147
3TA6 . . . . . V4-**T2**-188, V4-**T2**-190, V4-**T2**-203, V4-**T2**-311, V4-**T2**-336, V4-**T2**-347, V4-**T2**-355, V4-**T2**-356, V4-**T2**-393
3T1 . . . . . V4-**T2**-24
3T10 . . . . . V4-**T2**-147, V4-**T2**-271, V4-**T2**-336, V4-**T2**-347, V4-**T2**-393
3T15 . . . . . V4-**T2**-147, V4-**T2**-336, V4-**T2**-393
3T2 . . . . . V4-**T2**-369
3T20 . . . . . V4-**T2**-147, V4-**T2**-358
3T22 . . . . . V4-**T2**-147
3T40 . . . . . V4-**T2**-179, V4-**T2**-393
3T6 . . . . . V4-**T2**-58
313C V4-**T2**-323
314C V4-**T2**-315, V4-**T2**-323, V4-**T2**-325, V4-**T2**-409
315C V4-**T2**-325
317B V4-**T3**-136
32B9 . . . . . V4-**T2**-323
373B V4-**T2**-323, V4-**T2**-409
374D V4-**T2**-323
38CL V4-**T3**-139
38RB V4-**T3**-102–V4-**T3**-107
38RD V4-**T3**-105–V4-**T3**-107
4ACLS V4-**T3**-130
4BCLS V4-**T3**-130
4CX V4-**T3**-140
4CXI V4-**T3**-140
4TA V4-**T2**-24, V4-**T2**-58, V4-**T2**-369
4TA4 . . . . . V4-**T2**-164, V4-**T2**-179, V4-**T2**-203
4TA6 . . . . . V4-**T2**-188, V4-**T2**-190, V4-**T2**-203, V4-**T2**-311
4T4 . . . . . V4-**T2**-369
4T40 . . . . . V4-**T2**-179
4T6 . . . . . V4-**T2**-58, V4-**T2**-369
4210 . . . . . V4-**T2**-314
4212 . . . . . V4-**T2**-324
4217 . . . . . V4-**T2**-438
4218 . . . . . V4-**T2**-313
451D V4-**T2**-323
456D V4-**T2**-323, V4-**T2**-409
4995 . . . . . V4-**T2**-410
5ACLS V4-**T3**-130
5AHLE V4-**T3**-121
5BCLS V4-**T3**-130
5BHCL V4-**T3**-127
5BHLE V4-**T3**-121
5CLE V4-**T3**-118, V4-**T3**-134
5CLPT V4-**T3**-136
5CLS V4-**T3**-130, V4-**T3**-131
5CX V4-**T3**-140, V4-**T3**-141
5CXI V4-**T3**-141
5HCL V4-**T3**-127
5HCLS V4-**T3**-130
5HLE V4-**T3**-121, V4-**T3**-134
5LCL V4-**T3**-131
5NCLPT V4-**T3**-136
5RBA V4-**T3**-96–V4-**T3**-98
5010 . . . . . V4-**T2**-323
504C V4-**T2**-322
505C V4-**T2**-325
506C V4-**T2**-321, V4-**T2**-322, V4-**T2**-325
507C V4-**T2**-321
510 . . . . . V4-**T2**-36, V4-**T2**-52, V4-**T2**-69, V4-**T2**-81, V4-**T2**-328
5108 . . . . . V4-**T2**-106, V4-**T2**-150, V4-**T2**-328
5652 . . . . . V4-**T2**-25, V4-**T2**-312
5672 . . . . . V4-**T2**-410
5685 . . . . . V4-**T2**-404–V4-**T2**-407
6DSL V4-**T3**-147
623B V4-**T2**-323, V4-**T2**-409
624B V4-**T2**-259, V4-**T2**-312, V4-**T2**-313, V4-**T2**-324, V4-**T2**-325, V4-**T2**-408
625B V4-**T2**-314
656D V4-**T2**-409
66A V4-**T2**-423, V4-**T2**-434
6631 . . . . . V4-**T2**-314
6636 . . . . . V4-**T2**-322
6641 . . . . . V4-**T2**-314
6642 . . . . . V4-**T2**-323
6648 . . . . . V4-**T2**-438
673B V4-**T2**-324
68C V4-**T2**-421, V4-**T2**-423, V4-**T2**-435
69D V4-**T2**-423, V4-**T2**-434
7ACLS V4-**T3**-132
7BCLS V4-**T3**-131
7CLS V4-**T3**-131, V4-**T3**-132
752B V4-**T2**-418
8ACLS V4-**T3**-131
8AHLE V4-**T3**-122
8BHLE V4-**T3**-122
8CLE V4-**T3**-119, V4-**T3**-134
8CLP V4-**T3**-137
8CLPT V4-**T3**-137
8CLS V4-**T3**-131, V4-**T3**-132
8CX V4-**T3**-142, V4-**T3**-146
8CXI V4-**T3**-142
8CXN V4-**T3**-144
8HLE V4-**T3**-122, V4-**T3**-134
8NCL V4-**T3**-137
8RBA V4-**T3**-96–V4-**T3**-98
8RBT V4-**T3**-96–V4-**T3**-98
8RDB V4-**T3**-96–V4-**T3**-98
8703 . . . . . V4-**T2**-312

A

Accessories
- Expulsion Fuses
  - End Fittings V4-**T3**-94
  - Live Parts V4-**T3**-94
  - Mountings V4-**T3**-94
- Industrial Circuit Breakers, QUICKLAG V4-**T1**-27
  - Dummy Breakers V4-**T1**-45
  - Factory Modifications V4-**T1**-46
  - Handle Locks V4-**T1**-43
  - Handle Tie V4-**T1**-45
  - Mounting Hardware V4-**T1**-44
  - Quick-Connect Terminals V4-**T1**-27
  - Ring or Spade Lug Terminals V4-**T1**-27
  - Spare Terminal Hardware Screws V4-**T1**-46
  - Standard Box Terminals V4-**T1**-27
- Medium Voltage Power Contactors
  - Mechanical Latch V4-**T3**-84, V4-**T3**-88
- Molded Case Circuit Breakers, Definite Purpose
  - Base Mounting Hardware V4-**T2**-336
  - End Cap Accessory Kit V4-**T2**-336
  - Line and Load Terminals V4-**T2**-336
- Molded Case Circuit Breakers, Series C, External
  - Auxiliary Power Module V4-**T2**-327
  - Base Mounting Hardware V4-**T2**-312
  - Base Mounting Plate V4-**T2**-315
  - Breaker Interface Module (BIM) V4-**T2**-327
  - Cause of Trip Display/Remote Mount Cause of Trip Display V4-**T2**-327
  - Cause of Trip LED Module V4-**T2**-327
  - Cylinder Lock V4-**T2**-317
  - Digitrip OPTIMizer V4-**T2**-327
  - DIN Rail Adapter V4-**T2**-315
  - Direct (Close-Coupled) Handle Mechanisms V4-**T2**-259, V4-**T2**-442
  - Electrical Operator V4-**T2**-320
  - Flex Shaft Accessories (F- through R-Frame) V4-**T2**-328
  - Ground Fault Alarm Unit V4-**T2**-326
  - Handle Extension V4-**T2**-446
  - Interphase Barriers V4-**T2**-315
  - IQ Energy Sentinel V4-**T2**-326
  - Key Interlock Kit V4-**T2**-318
  - Key Operated Attachment V4-**T2**-315
  - Lock Dog (Non-Padlockable) V4-**T2**-316
  - Non-Padlockable Handle Block V4-**T2**-316
  - Padlockable Handle V4-**T2**-316
  - Padlockable Handle Lock V4-**T2**-316
  - Padlockable Handle Lock Hasp V4-**T2**-317
  - Panelboard Connecting Straps V4-**T2**-324
  - Plug-In Adapters V4-**T2**-321
  - Potential Transformer Module V4-**T2**-326
  - Rear Connected Studs V4-**T2**-323
  - Series C Rotary Accessories V4-**T2**-328
  - Sliding Bar Interlock V4-**T2**-319
  - Snap-On Padlockable Handle Lock Hasp V4-**T2**-316
  - Solid-State (Electronic) Test Kit V4-**T2**-326
  - Terminal End Covers V4-**T2**-315
  - Terminal Shields V4-**T2**-314

Accessories, continued
- Molded Case Circuit Breakers, Series C, External, continued
  - Termination Hardware V4-**T2**-310
  - Type LFD Current Limiter V4-**T2**-326
  - Walking Beam Interlock V4-**T2**-319
- Molded Case Circuit Breakers, Series C, Internal
  - Alarm Switch V4-**T2**-275
  - Auxiliary/Alarm Switch Combination V4-**T2**-279
  - Shunt Trip V4-**T2**-281
  - Terminal Block V4-**T2**-293
  - Undervoltage Release Mechanism V4-**T2**-286–V4-**T2**-292
  - Zone Interlock Kits V4-**T2**-293
- Molded Case Circuit Breakers, Series G, External
  - Electrical Operator V4-**T2**-107
  - Handle Blocks V4-**T2**-107
  - Handle Lock Hasps V4-**T2**-107
  - Interlock Kits V4-**T2**-107
  - Plug-In Adapters V4-**T2**-107
  - Rear Wohner busbar adpater V4-**T2**-107
- Molded Case Circuit Breakers, Series G, Internal
  - Alarm Lockout V4-**T2**-109
  - Auxiliary Switch V4-**T2**-109
  - Auxiliary Switch/Alarm Lockout V4-**T2**-109
  - Shunt Trip—Low Energy V4-**T2**-110
  - Shunt Trip—Standard V4-**T2**-110
  - Undervoltage Release Mechanism V4-**T2**-110
- Molded Case Circuit Breakers, Specialty Breakers, Add-On Ground Fault Protection
  - Ammeter Kit V4-**T2**-418
  - Face Plate V4-**T2**-418
  - Ground Fault Warning Indicator V4-**T2**-418
  - Test Panel V4-**T2**-418
- Molded Case Circuit Breakers, Specialty Breakers, Classic Mining Breakers
  - Line and Load Terminal Shields V4-**T2**-409
  - Rear Connected Studs V4-**T2**-409
  - Shunt Trip V4-**T2**-410
  - Undervoltage Release Mechanism V4-**T2**-410
- Molded Case Circuit Breakers, Specialty Breakers, Direct Current
  - Auxiliary Switch V4-**T2**-359
  - Shunt Trip V4-**T2**-359
  - Undervoltage Release Mechanism V4-**T2**-359
- Molded Case Circuit Breakers, Specialty Breakers, E^2 Mining Service
  - Alarm (Signal/Lockout Switch) V4-**T2**-395
  - Auxiliary Switch V4-**T2**-395
  - End Cap Terminals V4-**T2**-393
  - Line and Load Terminals V4-**T2**-393
  - Padlockable Handle Lock Hasp V4-**T2**-393
  - Shunt Trip V4-**T2**-395
  - Undervoltage Release Mechanism V4-**T2**-394
- Molded Case Circuit Breakers, Specialty Breakers, Engine Generator
  - Auxiliary Switch V4-**T2**-347
  - Neutral Kits V4-**T2**-347
  - Shunt Trip V4-**T2**-347
  - Standard Terminals V4-**T2**-347

Appendix 3—Alphabetical Product Index

Accessories, continued
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Photovoltaic
Alarm Switch . . . V4-**T2**-368
Auxiliary and Alarm Combo . . . V4-**T2**-368
Auxiliary Switch . . . V4-**T2**-368
End Cap Kits . . . V4-**T2**-369
Imperial Base Mounting Hardware . . . V4-**T2**-367
Interphase Barrier . . . V4-**T2**-367
Metric Base Mounting Hardware . . . V4-**T2**-367
Non-Padlockable Handle Block . . . V4-**T2**-367
Padlockable Handle Lock Hasp . . . V4-**T2**-367
PVGard Solar Circuit Breaker Terminal . . . V4-**T2**-369
Shunt Trip . . . V4-**T2**-368
Undervoltage Release . . . V4-**T2**-368
Power Circuit Breakers, Magnum . . . V4-**T3**-30
Auxiliary Switch . . . V4-**T3**-30
Bell Alarm/Overcurrent Trip Switch . . . V4-**T3**-30
Key Off Lock Provisions . . . V4-**T3**-30
Latch Check Switch . . . V4-**T3**-30
Mechanical Operations Counter . . . V4-**T3**-30
Mechanical Trip Indicator Flag . . . V4-**T3**-30
Padlockable Pushbutton Cover . . . V4-**T3**-30
Shunt Trip Device . . . V4-**T3**-30
Spring Charge Motor . . . V4-**T3**-30
Spring Release Device . . . V4-**T3**-30
Undervoltage Release . . . V4-**T3**-30
UL 1053 DIN Rail RCCB 208Y/120 Vac . . . V4-**T1**-98
Contact . . . V4-**T1**-98
Padlock Hasp . . . V4-**T1**-98
Protective Accessories . . . V4-**T1**-98
UL 1053 DIN Rail RCCB 480/277 Vac . . . V4-**T1**-92
Contact . . . V4-**T1**-92
Padlock Hasp . . . V4-**T1**-92
Protective Accessories . . . V4-**T1**-92
UL 1077 DIN Rail Supplementary Protectors, FAZ . . . V4-**T1**-78
Auxiliary Contact . . . V4-**T1**-78
Busbar End Cap . . . V4-**T1**-80
Busbar System . . . V4-**T1**-79
Contact . . . V4-**T1**-78
Protective Accessories . . . V4-**T1**-80
Supply Terminals . . . V4-**T1**-80
Voltage Trips . . . V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ
Shunt Trip . . . V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA . . . V4-**T1**-58
Auxiliary Contact . . . V4-**T1**-58
Bus Connector . . . V4-**T1**-58
Busbar . . . V4-**T1**-58
Busbar Shroud . . . V4-**T1**-58
Contact . . . V4-**T1**-58
Extension Terminal . . . V4-**T1**-58
Padlock Hasp . . . V4-**T1**-58
Protective Accessories . . . V4-**T1**-58
Shunt Trip . . . V4-**T1**-58
Supply Terminals . . . V4-**T1**-58
UL Lockoff Device . . . V4-**T1**-58
Voltage Trips . . . V4-**T1**-58

Accessories, Digitrip 310+ Electronic Trip Unit
Molded Case Circuit Breakers, Series G
Electronic Portable Test Kit . . . V4-**T2**-106
Wire Seal . . . V4-**T2**-106
Add-On Ground Fault Protection—Type GFR
Molded Case Circuit Breakers, Specialty . . . V4-**T2**-416
Alarm (Signal/Lockout Switch)
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service
Accessories . . . V4-**T2**-395
Alarm Lockout
Molded Case Circuit Breakers, Series G, Internal
Accessories . . . V4-**T2**-109
Alarm Switch
Molded Case Circuit Breakers, Series C, Internal
Accessories . . . V4-**T2**-275
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Photovoltaic Circuit Breakers
Accessories . . . V4-**T2**-368
Ammeter Kit
Molded Case Circuit Breakers, Add-On Ground Fault Protection
Accessories . . . V4-**T2**-418
Auxiliary and Alarm Combo
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Photovoltaic Circuit Breakers
Accessories . . . V4-**T2**-368
Auxiliary Contact
UL 1077 DIN Rail Supplementary Protectors, FAZ
Accessories . . . V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA
Accessories . . . V4-**T1**-58
Auxiliary Power Module
Molded Case Circuit Breakers, Series C, External
Accessories . . . V4-**T2**-327
Auxiliary Switch
Molded Case Circuit Breakers, Series C, Internal
Accessories . . . V4-**T2**-277
Molded Case Circuit Breakers, Series G, Internal
Accessories . . . V4-**T2**-109
Molded Case Circuit Breakers, Speciality Breakers, Direct Current
Accessories . . . V4-**T2**-359
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service
Accessories . . . V4-**T2**-395
Molded Case Circuit Breakers, Specialty Breakers, Engine Generator
Accessories . . . V4-**T2**-347
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Photovoltaic Circuit Breakers
Accessories . . . V4-**T2**-368
Power Circuit Breakers, Magnum
Accessories . . . V4-**T3**-30

Auxiliary Switch and Alarm Switch Combination
Molded Case Circuit Breakers, Series C, Internal Accessories V4-**T2**-279
Auxiliary Switch/Alarm Lockout
Molded Case Circuit Breakers, Series G, Internal Accessories V4-**T2**-109

B

Base Mounting Hardware
Molded Case Circuit Breakers, Definite Purpose Accessories V4-**T2**-336
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-312
Base Mounting Plate
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-315
Bell Alarm/Overcurrent Trip Switch
Power Circuit Breakers, Magnum Accessories V4-**T3**-30
Bolt-On, QUICKLAG
Industrial Circuit Breakers V4-**T1**-11, V4-**T1**-14, V4-**T1**-17
Breaker Interface Module (BIM)
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-327
Bus Connector
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58
Busbar
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58
Busbar End Cap
UL 1077 DIN Rail Supplementary Protectors, FAZ Accessories V4-**T1**-80
Busbar Shroud
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58
Busbar System
UL 1077 DIN Rail Supplementary Protectors, FAZ Accessories V4-**T1**-79

C

Cable-In/Cable-Out, QUICKLAG
Industrial Circuit Breakers V4-**T1**-20, V4-**T1**-24, V4-**T1**-28
Cause of Trip Display/Remote Mount Cause of Trip Display
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-327
Cause of Trip LED Module
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-327
Classic Mining Breakers
Molded Case Circuit Breakers, Specialty V4-**T2**-402
Contact
UL 1053 DIN Rail RCCB 208Y/120 Vac Accessories V4-**T1**-98
UL 1053 DIN Rail RCCB 480/277 Vac Accessories V4-**T1**-92
UL 1077 DIN Rail Supplementary Protectors, FAZ Accessories V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58
Current Limiting Circuit Breaker Module
Molded Case Circuit Breakers, Series C V4-**T2**-270
Molded Case Circuit Breakers, Series G V4-**T2**-96
Current Limiting Fuses
Power Breakers, Contactors & Fuses . . . V4-**T3**-115–V4-**T3**-148
Type BHLE V4-**T3**-124
Type CLE V4-**T3**-117
Type CLPT V4-**T3**-135
Type CLS V4-**T3**-129
Type CX V4-**T3**-140
Type CXF V4-**T3**-146
Type CXN V4-**T3**-144
Type DSL V4-**T3**-147
Type HCL V4-**T3**-127
Type HLE V4-**T3**-121
Cylinder Lock
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-317

D

Definite Purpose Breakers
Molded Case Circuit Breakers V4-**T2**-333–V4-**T2**-339
GP-, FP-, KP-, LP-, MP-Frames V4-**T2**-333
Digitrip OPTIMizer
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-327
DIN Rail Adapter
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-315
Direct (Close-Coupled) Handle Mechanisms
Handle Mechanisms—Series C Molded Case Circuit Breakers V4-**T2**-441
Handle Mechanisms—Series G Molded Case Circuit Breakers V4-**T2**-427
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-259, V4-**T2**-442
Direct Current Circuit Breakers
Molded Case Circuit Breakers, Specialty V4-**T2**-349
Drawout Cassette
Molded Case Circuit Breakers, Series G V4-**T2**-115
Dummy Breakers
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-45

Appendix 3—Alphabetical Product Index

E

E^2 Mining Service Breakers
Molded Case Circuit Breakers, Specialty V4-**T2**-376
Eaton Terms & Conditions V4-**A1**-1
Freight V4-**A1**-3
Limitation of Liability V4-**A1**-5
Terms and Conditions of Sale V4-**A1**-1
Terms of Payment. V4-**A1**-2
Warranty V4-**A1**-3
EG-Frame (15–125 Amperes)
Molded Case Circuit Breakers, Series G V4-**T2**-15
Electrical Operator
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-320
Molded Case Circuit Breakers, Series G, External Accessories V4-**T2**-107
Electronic Portable Test Kit
Molded Case Circuit Breakers, Series G Accessories, Digitrip 310+ Electronic Trip Unit . . . V4-**T2**-106
End Cap Accessory Kit
Molded Case Circuit Breakers, Definite Purpose Accessories V4-**T2**-336
End Cap Terminals
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service Accessories V4-**T2**-393
End Fittings
Expulsion Fuses
Accessories V4-**T3**-94
Endcap Kits
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Circuit Breakers Accessories V4-**T2**-369
Engine Generator Circuit Breakers
Molded Case Circuit Breakers, Specialty V4-**T2**-343
Expulsion Fuses
Power Breakers, Contactors & Fuses V4-**T3**-94–V4-**T3**-114
Accessories V4-**T3**-94
Type DBU V4-**T3**-108
Type RBA and RDB V4-**T3**-96
Extension Terminal
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58

F

Face Plate
Molded Case Circuit Breakers, Add-On Ground Fault Protection Accessories V4-**T2**-418
Factory Modifications
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-46
FAZ
UL 1077 DIN Rail Supplementary Protectors
Miniature Circuit Breakers and Supplementary Protectors V4-**T1**-70–V4-**T1**-89
FAZ-NA
UL 489 DIN Rail Miniature Circuit Breakers
Miniature Circuit Breakers and Supplementary Protectors V4-**T1**-49–V4-**T1**-69
F-Frame (10–225 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-135
Flex Shaft
Handle Mechanisms—Series C
Molded Case Circuit Breakers V4-**T2**-443
Handle Mechanisms—Series G
Molded Case Circuit Breakers V4-**T2**-428
Flex Shaft Accessories (F- through R-Frame)
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-328
FP-Frame
Molded Case Circuit Breakers, Definite Purpose . . . V4-**T2**-333
Fuses
Current Limiting V4-**T3**-115–V4-**T3**-148
Expulsion V4-**T3**-94–V4-**T3**-96
General V4-**T3**-91

G

G-Frame (15–100 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-121
GP-Frame
Molded Case Circuit Breakers, Definite Purpose . . . V4-**T2**-333
Ground Fault (Earth Leakage) Modules
Molded Case Circuit Breakers, Series G V4-**T2**-92
Ground Fault Alarm Unit
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-326
Ground Fault Warning Indicator
Molded Case Circuit Breakers, Add-On Ground Fault Protection Accessories. V4-**T2**-418

H

Handle Blocks
Molded Case Circuit Breakers, Series G, External Accessories. V4-**T2**-107
Handle Extension
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-446
Handle Lock Hasp
Molded Case Circuit Breakers, Series G, External Accessories. V4-**T2**-107
Handle Locks
Industrial Circuit Breakers, QUICKLAG Accessories. V4-**T1**-43

Handle Mechanisms
Molded Case Circuit Breakers V4-**T2**-419–V4-**T2**-446
Handle Mechanisms—Series C
Molded Case Circuit Breakers, Direct (Close-Coupled) Handle Mechanisms. V4-**T2**-441
Molded Case Circuit Breakers, Flex Shaft V4-**T2**-443
Molded Case Circuit Breakers, Handle Mechanisms. V4-**T2**-431
Molded Case Circuit Breakers, High-Performance Rotary Handle Mechanisms V4-**T2**-433
Molded Case Circuit Breakers, Series C Rotary V4-**T2**-437
Molded Case Circuit Breakers, Through-the-Door Handle Mechanisms. V4-**T2**-438
Molded Case Circuit Breakers, Universal Rotary . . . V4-**T2**-439
Handle Mechanisms—Series G
Molded Case Circuit Breakers, Direct (Close-Coupled) Handle Mechanisms. V4-**T2**-427
Molded Case Circuit Breakers, Flex Shaft V4-**T2**-428
Molded Case Circuit Breakers, Handle Mechanisms. V4-**T2**-419
Molded Case Circuit Breakers, High-Performance Rotary Handle Mechanisms V4-**T2**-420
Molded Case Circuit Breakers, Universal Rotary . . . V4-**T2**-425
Handle Tie
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-45
High Instantaneous Circuit Breaker
Molded Case Circuit Breakers, Series G. V4-**T2**-101
High-Performance Rotary Handle Mechanisms
Handle Mechanisms—Series C Molded Case Circuit Breakers V4-**T2**-433
Handle Mechanisms—Series G Molded Case Circuit Breakers V4-**T2**-420

I

Imperial Base Mounting Hardware
Molded Case Circuit Breakers, Specialty Breakers, PVGard Solar Circuit Breakers Accessories V4-**T2**-367
Industrial Circuit Breakers, QUICKLAG
Accessories. V4-**T1**-27, V4-**T1**-43
Bolt-On V4-**T1**-11, V4-**T1**-14, V4-**T1**-17
Cable-In/Cable-Out V4-**T1**-20, V4-**T1**-24, V4-**T1**-28
International Rated V4-**T1**-37
Plug-On V4-**T1**-5–V4-**T1**-10
Solenoid-Operated V4-**T1**-31, V4-**T1**-34
Special Application Breakers. V4-**T1**-40
Interlock Kits
Molded Case Circuit Breakers, Series G, External Accessories V4-**T2**-107
International Rated, QUICKLAG
Industrial Circuit Breakers. V4-**T1**-37
Interphase Barriers
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-315
Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers Accessories. V4-**T2**-367
IQ Energy Sentinel
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-326

J

J-Frame (70–250 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-153
JG-Frame (63–250 Amperes)
Molded Case Circuit Breakers, Series G V4-**T2**-29

K

Key Interlock Kit
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-318
Key Off Lock Provisions
Power Circuit Breakers, Magnum Accessories. V4-**T3**-30
Key Operated Attachment
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-315
K-Frame (70–400 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-161
KP-Frame
Molded Case Circuit Breakers, Definite Purpose . . . V4-**T2**-333

L

Latch Check Switch
Power Circuit Breakers, Magnum Accessories. V4-**T3**-30
L-Frame (125–600 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-185
LG-Frame (250–630 Amperes)
Molded Case Circuit Breakers, Series G V4-**T2**-47
Line and Load Terminal Shields
Molded Case Circuit Breakers, Speciality Breakers, Classic Mining Service Accessories. V4-**T2**-409
Line and Load Terminals
Molded Case Circuit Breakers, Definite Purpose Accessories. V4-**T2**-336
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service Accessories. V4-**T2**-393
Live Parts
Expulsion Fuses Accessories. V4-**T3**-94

Lock Dog (Non-Padlockable)
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-316
LP-Frame
Molded Case Circuit Breakers, Definite Purpose . . . V4-**T2**-333

M

Magnum DC (Direct Current) Low Voltage Switches
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-33
Magnum DS Low Voltage Power Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-6
Magnum IEC Rated Air Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-23
Magnum MDSL Current Limiting Power Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-12
Magnum SB Low Voltage Insulated Case Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-15
Mechanical Latch
Medium Voltage Power Contactors
Accessories V4-**T3**-84
Mechanical Operations Counter
Power Circuit Breakers, Magnum
Accessories V4-**T3**-30
Mechanical Trip Indicator Flag
Power Circuit Breakers, Magnum
Accessories V4-**T3**-30
Medium Voltage Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-55
Medium Voltage Power Contactors
Power Breakers, Contactors & Fuses
Accessories V4-**T3**-84, V4-**T3**-88
SL MV Power Contactor. V4-**T3**-74, V4-**T3**-83, V4-**T3**-87
Metering and Communications
Molded Case Circuit Breakers
PM3 Monitoring and Metering Module V4-**T2**-340
Metric Base Mounting Hardware
Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers
Accessories V4-**T2**-367
M-Frame (300–800 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-211
Miniature Circuit Breakers and Supplementary Protectors V4-**T1**-1–V4-**T1**-101
Industrial Circuit Breakers
QUICKLAG V4-**T1**-2–V4-**T1**-48
UL 1077 DIN Rail Supplementary Protectors
FAZ V4-**T1**-70–V4-**T1**-89
UL 489 DIN Rail Miniature Circuit Breakers
FAZ-NA V4-**T1**-49–V4-**T1**-69
Molded Case Circuit Breakers V4-**T2**-1–V4-**T2**-446
Definite Purpose Breakers. V4-**T2**-333–V4-**T2**-339
Handle Mechanisms V4-**T2**-419–V4-**T2**-446
Flex Shaft V4-**T2**-428
Handle Mechanisms—Series C V4-**T2**-431
Handle Mechanisms—Series G V4-**T2**-419
High-Performance Rotary Handle Mechanisms . . . V4-**T2**-420
Handle Mechanisms—Series C
Direct (Close-Coupled) Handle Mechanisms V4-**T2**-441
Flex Shaft V4-**T2**-443
High-Performance Rotary Handle Mechanisms . . . V4-**T2**-433
Series C Rotary V4-**T2**-437
Through-the-Door Handle Mechanisms V4-**T2**-438
Universal Rotary V4-**T2**-439
Handle Mechanisms—Series G
Direct (Close-Coupled) Handle Mechanisms V4-**T2**-427
Universal Rotary V4-**T2**-425
Introduction V4-**T2**-2, V4-**T2**-3
Metering and Communications V4-**T2**-340–V4-**T2**-342
Series C V4-**T2**-116–V4-**T2**-332
Series G V4-**T2**-4–V4-**T2**-115
Specialty Breakers V4-**T2**-343–V4-**T2**-418
Motor Circuit Protectors
Molded Case Circuit Breakers, Series G V4-**T2**-85
Motor Circuit Protectors (MCP)
Molded Case Circuit Breakers, Series C V4-**T2**-256
Motor Operators
Molded Case Circuit Breakers, Series G V4-**T2**-112
Motor Protection Circuit Breakers
Molded Case Circuit Breakers, Series C V4-**T2**-267
Molded Case Circuit Breakers, Series G V4-**T2**-89
Mounting Hardware
Industrial Circuit Breakers, QUICKLAG Accessories. V4-**T1**-44
Mountings
Expulsion Fuses
Accessories. V4-**T3**-94
MP-Frame
Molded Case Circuit Breakers, Definite Purpose . . . V4-**T2**-333

N

Neutral Kits
Molded Case Circuit Breakers, Specialty Breakers, Engine Generator
Accessories. V4-**T2**-347
N-Frame (400–1200 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-222
NG-Frame (320–1200 Amperes)
Molded Case Circuit Breakers, Series G V4-**T2**-65
Non-Padlockable Handle Block
Molded Case Circuit Breakers, Series C, External Accessories. V4-**T2**-316
Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers
Accessories. V4-**T2**-367

P

Padlock Hasp
- UL 1053 DIN Rail RCCB 208Y/120 Vac Accessories . . . V4-**T1**-98
- UL 1053 DIN Rail RCCB 480/277 Vac Accessories . . . V4-**T1**-92
- UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories . . . V4-**T1**-58

Padlockable Handle
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-316

Padlockable Handle Lock
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-316

Padlockable Handle Lock Hasp
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-317
- Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service Accessories . . . V4-**T2**-393
- Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers Accessories . . . V4-**T2**-367

Padlockable Pushbutton Cover
- Power Circuit Breakers, Magnum Accessories . . . V4-**T3**-30

Panelboard Connecting Straps
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-324

Plug-In Adapters
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-321
- Molded Case Circuit Breakers, Series G, External Accessories . . . V4-**T2**-107

Plug-In Blocks
- Molded Case Circuit Breakers, Series G . . . V4-**T2**-114

Plug-On, QUICKLAG
- Industrial Circuit Breakers . . . V4-**T1**-5–V4-**T1**-10

PM3 Monitoring and Metering Module
- Molded Case Circuit Breakers, Metering and Communications . . . V4-**T2**-340

Potential Transformer Module
- Molded Case Circuit Breakers, Series C, External Accessories . . . V4-**T2**-326

Power Breakers, Contactors & Fuses . . . V4-**T3**-1–V4-**T3**-148
- Current Limiting Fuses . . . V4-**T3**-115–V4-**T3**-148
  - Type BHLE . . . V4-**T3**-124
  - Type CLE . . . V4-**T3**-117
  - Type CLPT . . . V4-**T3**-135
  - Type CLS . . . V4-**T3**-129
  - Type CX . . . V4-**T3**-140
  - Type CXF . . . V4-**T3**-146
  - Type CXN . . . V4-**T3**-144
  - Type DSL . . . V4-**T3**-147
  - Type HCL . . . V4-**T3**-127
  - Type HLE . . . V4-**T3**-121

Power Breakers, Contactors & Fuses, continued
- Expulsion Fuses . . . V4-**T3**-94–V4-**T3**-114
  - Accessories . . . V4-**T3**-94
  - Type DBU . . . V4-**T3**-108
  - Type RBA and RDB . . . V4-**T3**-96
- Fuses . . . V4-**T3**-91–V4-**T3**-93
- Medium Voltage Power Contactors . . . V4-**T3**-72–V4-**T3**-90
  - Accessories . . . V4-**T3**-84, V4-**T3**-88
  - SL MV Power Contactor . . . V4-**T3**-74, V4-**T3**-83, V4-**T3**-87
- Power Circuit Breakers . . . V4-**T3**-2–V4-**T3**-71
  - Low Voltage Power Circuit Breakers . . . V4-**T3**-2
  - Magnum DC (Direct Current) Low Voltage Switches . . . V4-**T3**-33
  - Magnum DS Low Voltage Power Circuit Breakers . . . V4-**T3**-6
  - Magnum IEC Rated Air Circuit Breakers . . . V4-**T3**-23
  - Magnum MDSL Current Limiting Power Circuit Breakers . . . V4-**T3**-12
  - Magnum SB Low Voltage Insulated Case Circuit Breakers . . . V4-**T3**-15
  - Medium Voltage Circuit Breakers . . . V4-**T3**-55
  - Series NRX Low Voltage Power Circuit Breakers . . . V4-**T3**-35, V4-**T3**-47
- Power Circuit Breakers, Magnum Accessories . . . V4-**T3**-30

Power Circuit Breakers
- Power Breakers, Contactors & Fuses
  - Low Voltage Power Circuit Breakers . . . V4-**T3**-2
  - Magnum DC (Direct Current) Low Voltage Switches . . . V4-**T3**-33
  - Magnum DS Low Voltage Power Circuit Breakers . . . V4-**T3**-6
  - Magnum IEC Rated Air Circuit Breakers . . . V4-**T3**-23
  - Magnum MDSL Current Limiting Power Circuit Breakers . . . V4-**T3**-12
  - Magnum SB Low Voltage Insulated Case Circuit Breakers . . . V4-**T3**-15
  - Medium Voltage Circuit Breakers . . . V4-**T3**-55
  - Series NRX Low Voltage Power Circuit Breakers . . . V4-**T3**-35, V4-**T3**-47

Protective Accessories
- UL 1053 DIN Rail RCCB 208Y/120 Vac Accessories . . . V4-**T1**-98
- UL 1053 DIN Rail RCCB 480/277 Vac Accessories . . . V4-**T1**-92
- UL 1077 DIN Rail Supplementary Protectors, FAZ Accessories . . . V4-**T1**-80
- UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories . . . V4-**T1**-58

PVGard Solar Circuit Breaker Terminal
- Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers Accessories . . . V4-**T2**-369

PVGard Solar Circuit Breakers
- Molded Case Circuit Breakers, Specialty . . . V4-**T2**-363

Q

Quick-Connect Terminals
- Industrial Circuit Breakers, QUICKLAG Accessories . . . V4-**T1**-27

QUICKLAG
Industrial Circuit Breakers V4-**T1**-2–V4-**T1**-48
Accessories V4-**T1**-27, V4-**T1**-43
Bolt-On V4-**T1**-11, V4-**T1**-14, V4-**T1**-17
Cable-In/Cable-Out V4-**T1**-20, V4-**T1**-24, V4-**T1**-28
International Rated V4-**T1**-37
Plug-On V4-**T1**-5–V4-**T1**-10
Solenoid-Operated V4-**T1**-31, V4-**T1**-34
Special Application Breakers V4-**T1**-40

R

Rear Connected Studs
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-323
Molded Case Circuit Breakers, Speciality Breakers, Classic Mining Service Accessories V4-**T2**-409
R-Frame (800–2500 Amperes)
Molded Case Circuit Breakers, Series C V4-**T2**-237
RG-Frame (800–2500 Amperes)
Molded Case Circuit Breakers, Series G V4-**T2**-74
Ring or Spade Lug Terminals
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-27

S

Series C
Molded Case Circuit Breakers V4-**T2**-116–V4-**T2**-332
Current Limiting Circuit Breaker Module V4-**T2**-270
External Accessories V4-**T2**-306
F-Frame (10–225 Amperes) V4-**T2**-135
G-Frame (15–100 Amperes) V4-**T2**-121
Internal Accessories V4-**T2**-273
J-Frame (70–250 Amperes) V4-**T2**-153
K-Frame (70–400 Amperes) V4-**T2**-161
L-Frame (125–600 Amperes) V4-**T2**-185
M-Frame (300–800 Amperes) V4-**T2**-211
Motor Circuit Protectors (MCP) V4-**T2**-256
Motor Protection Circuit Breakers V4-**T2**-267
N-Frame (400–1200 Amperes) V4-**T2**-222
R-Frame (800–2500 Amperes) V4-**T2**-237
Type ELC Current Limiter Attachment V4-**T2**-269
Series C Rotary
Handle Mechanisms—Series C Molded Case Circuit Breakers V4-**T2**-437
Series C Rotary Accessories
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-328
Series G
Molded Case Circuit Breakers V4-**T2**-4–V4-**T2**-115
Current Limiting Circuit Breaker Module V4-**T2**-96
Drawout Cassette V4-**T2**-115
EG-Frame (15–125 Amperes) V4-**T2**-15
Ground Fault (Earth Leakage) Modules V4-**T2**-92
High Instantaneous Circuit Breaker V4-**T2**-101
JG-Frame (63–250 Amperes) V4-**T2**-29
LG-Frame (250–630 Amperes) V4-**T2**-47
Series G, continued
Molded Case Circuit Breakers, continued
Motor Circuit Protectors V4-**T2**-85
Motor Operators V4-**T2**-112
Motor Protection Circuit Breaker V4-**T2**-89
NG-Frame (320–1200 Amperes) V4-**T2**-65
Plug-In Blocks V4-**T2**-114
RG-Frame (800–2500 Amperes) V4-**T2**-74
Special Features and Accessories V4-**T2**-104
Series NRX Low Voltage Power Circuit Breakers
Power Circuit Breakers
Power Breakers, Contactors & Fuses V4-**T3**-35, V4-**T3**-47
Shunt Trip
Molded Case Circuit Breakers, Series C, Internal Accessories V4-**T2**-281
Molded Case Circuit Breakers, Speciality Breakers, Classic Mining Service Accessories V4-**T2**-410
Molded Case Circuit Breakers, Speciality Breakers, Direct Current Accessories V4-**T2**-359
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service Accessories V4-**T2**-395
Molded Case Circuit Breakers, Specialty Breakers, Engine Generator Accessories V4-**T2**-347
Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers Accessories V4-**T2**-368
UL 489 DIN Rail Miniature Circuit Breakers, FAZ Accessories V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58
Shunt Trip Device
Power Circuit Breakers, Magnum Accessories V4-**T3**-30
Shunt Trip—Low Energy
Molded Case Circuit Breakers, Series G, Internal Accessories V4-**T2**-110
Shunt Trip—Standard
Molded Case Circuit Breakers, Series G, Internal Accessories V4-**T2**-110
SL MV Power Contactor
Medium Voltage Power Contactors
Power Breakers, Contactors & Fuses V4-**T3**-74, V4-**T3**-83, V4-**T3**-87
Sliding Bar Interlock
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-319
Snap-On Padlockable Handle Lock Hasp
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-316
Solenoid-Operated, QUICKLAG
Industrial Circuit Breakers V4-**T1**-31, V4-**T1**-34

Solid-State (Electronic) Portable Test Kit
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-326
Spare Terminal Hardware Screws
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-46
Special Application Breakers, QUICKLAG
Industrial Circuit Breakers V4-**T1**-40
Specialty Breakers
Molded Case Circuit Breakers V4-**T2**-343–V4-**T2**-418
Add-On Ground Fault Protection—Type GFR V4-**T2**-416
Classic Mining Breakers V4-**T2**-402
Direct Current Circuit Breakers V4-**T2**-349
E^2 Mining Service Circuit Breakers V4-**T2**-376
Engine Generator Circuit Breakers V4-**T2**-343
PVGard Solar Circuit Breakers V4-**T2**-363
Spring Charge Motor
Power Circuit Breakers, Magnum Accessories V4-**T3**-30
Spring Release Device
Power Circuit Breakers, Magnum Accessories V4-**T3**-30
Standard Box Terminals
Industrial Circuit Breakers, QUICKLAG Accessories V4-**T1**-27
Standard Terminals
Molded Case Circuit Breakers, Specialty Breakers, Engine Generator Accessories V4-**T2**-347
Supplementary Protectors V4-**T1**-1–V4-**T1**-101
Supply Terminals
UL 1077 DIN Rail Supplementary Protectors, FAZ Accessories V4-**T1**-80
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA Accessories V4-**T1**-58

T

Terminal Block
Molded Case Circuit Breakers, Series C, Internal Accessories V4-**T2**-293
Terminal End Covers
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-315
Terminal Shields
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-314
Termination Hardware
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-310
Test Panel
Molded Case Circuit Breakers, Add-On Ground Fault Protection Accessories V4-**T2**-418
Type BHLE
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-124
Type CLE
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-117
Type CLPT
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-135
Type CLS
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-129
Type CX
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-140
Type CXF
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-146
Type CXN
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-144
Type DBU
Expulsion Fuses
Power Breakers, Contactors & Fuses V4-**T3**-108
Type DSL
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-147
Type ELC Current Limiter Attachment
Molded Case Circuit Breakers, Series C V4-**T2**-269
Type HCL
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-127
Type HLE
Current Limiting Fuses
Power Breakers, Contactors & Fuses V4-**T3**-121
Type LFD Current Limiter
Molded Case Circuit Breakers, Series C, External Accessories V4-**T2**-326
Type RBA and RDB
Expulsion Fuses
Power Breakers, Contactors & Fuses V4-**T3**-96

U

UL 1053 DIN Rail RCCB 208Y/120 Vac
Accessories V4-**T1**-98
Miniature Circuit Breakers and Supplementary Protectors V4-**T1**-96–V4-**T1**-101
UL 1053 DIN Rail RCCB 480/277 Vac
Accessories V4-**T1**-92
Miniature Circuit Breakers and Supplementary Protectors V4-**T1**-90–V4-**T1**-95
UL 1077 DIN Rail Supplementary Protectors, FAZ
Accessories V4-**T1**-78

Appendix 3—Alphabetical Product Index

UL 489 DIN Rail Miniature Circuit Breakers
Miniature Circuit Breakers and Supplementary Protectors
FAZ V4-**T1**-70–V4-**T1**-89
FAZ-NA V4-**T1**-49–V4-**T1**-69
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA
Accessories V4-**T1**-58
UL Lockoff Device
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA
Accessories V4-**T1**-58
Undervoltage Release
Molded Case Circuit Breakers, Speciality Breakers, PVGard Solar Circuit Breakers
Accessories V4-**T2**-368
Power Circuit Breakers, Magnum
Accessories V4-**T3**-30
Undervoltage Release Mechanism
Molded Case Circuit Breakers, Series C, Internal
Accessories V4-**T2**-286
Molded Case Circuit Breakers, Series G, Internal
Accessories V4-**T2**-110
Molded Case Circuit Breakers, Speciality Breakers, Classic Mining Service
Accessories V4-**T2**-410
Molded Case Circuit Breakers, Speciality Breakers, Direct Current
Accessories V4-**T2**-359
Molded Case Circuit Breakers, Speciality Breakers, E^2 Mining Service
Accessories V4-**T2**-394
Universal Rotary
Handle Mechanisms—Series C
Molded Case Circuit Breakers V4-**T2**-439
Handle Mechanisms—Series G
Molded Case Circuit Breakers V4-**T2**-425

V

Voltage Trips
UL 1077 DIN Rail Supplementary Protectors, FAZ
Accessories V4-**T1**-78
UL 489 DIN Rail Miniature Circuit Breakers, FAZ-NA
Accessories V4-**T1**-58

W

Walking Beam Interlock
Molded Case Circuit Breakers, Series C, External
Accessories V4-**T2**-319
Wire Seal
Molded Case Circuit Breakers, Series G
Accessories, Digitrip 310+ Electronic Trip Unit. . . . V4-**T2**-106
Wohner busbar adpater
Molded Case Circuit Breakers, Series G, External
Accessories V4-**T2**-107

Z

Zone Interlock Kits
Molded Case Circuit Breakers, Series C, Internal
Accessories V4-**T2**-293